


# EAO – Your Expert Partner for Human Machine Interfaces

## 61-3440.4/1 - Emergency-stop switch actuator, foolproof EN IEC 60947-5-5

### 61-3440.4/1 - Emergency-stop switch actuator, foolproof EN IEC 60947-5-5



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

#### Mounting

|                  |         |
|------------------|---------|
| Mounting cut-out | Ø 16 mm |
| Design           | raised  |

#### Front

|                 |         |
|-----------------|---------|
| Front shape     | round   |
| Front dimension | Ø 27 mm |

#### Other Attributes

|         |         |
|---------|---------|
| Marking | Arrows  |
| Weight  | 0.02 kg |

#### Operating-/Indication part

|               |          |
|---------------|----------|
| Lens material | Plastic  |
| Lens colour   | red      |
| Lens profile  | Mushroom |

#### IP-Rating

|                  |       |
|------------------|-------|
| Front protection | IP 65 |
|------------------|-------|

#### Actuator

|                  |            |
|------------------|------------|
| Switching action | Maintained |
|------------------|------------|


#### Function

|                       |
|-----------------------|
| Emergency stop switch |
|-----------------------|

# EAO – Your Expert Partner for Human Machine Interfaces


61-3440.4/1 - Emergency-stop switch actuator, foolproof EN IEC 60947-5-5

## Dimensions




L1 = Solder/Plug-in terminal 2.8 x 0.5 mm

## Mounting cut-outs



## Wiring diagram



## Additional information

Twist to unlock clockwise

Position indication ring black

Application as per DIN EN ISO 13850 and EN 60204-1

## Legend

Switching action: C = Maintained