

**W-Series  
WDU 6 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                                                                               |
|------------|-------------------------------------------------------------------------------|
| Type       | WDU 6 SL                                                                      |
| Order No.  | <a href="#">9537460000</a>                                                    |
| Version    | W-Series, Feed-through terminal, Rated cross-section: 6 mm², Screw connection |
| GTIN (EAN) | 4008190024222                                                                 |
| Qty.       | 50 pc(s).                                                                     |

**W-Series**  
**WDU 6 SL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|                          |          |                 |            |
|--------------------------|----------|-----------------|------------|
| Width                    | 7.9 mm   | Width (inches)  | 0.311 inch |
| Height                   | 60 mm    | Height (inches) | 2.362 inch |
| Depth                    | 46.5 mm  | Depth (inches)  | 1.831 inch |
| Depth including DIN rail | 47 mm    | Weight          | 16.57 g    |
| Net weight               | 16.226 g |                 |            |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | Dark Beige |
| UL 94 flammability rating | V-0   |        |            |

**Rating data IECEx/ATEX**

|                                |                   |                                 |                                                                                                   |
|--------------------------------|-------------------|---------------------------------|---------------------------------------------------------------------------------------------------|
| Certificate No. (ATEX)         | DEMKO14ATEX1338U  | ATEX certificate                | ACF-ATEX_4786180920.pdf                                                                           |
| Certificate No. (IECEX)        | IECEXULD14.0005U  | IEC Ex certificate              | IECEXSIR05.0040U_e.pdf                                                                            |
| Max. voltage (ATEX)            | 275 V             | Current (ATEX)                  | 40 A                                                                                              |
| Wire cross section max. (ATEX) | 6 mm <sup>2</sup> | Max. voltage (IECEX)            | 275 V                                                                                             |
| Current (IECEX)                | 40 A              | Wire cross section max. (IECEX) | 6 mm <sup>2</sup>                                                                                 |
| Voltage, cross-connection      |                   | Operating temperature range     | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity |
| Marking EN 60079-7             | Ex e II           | Ex 2014/34/EU label             | II 2 G D                                                                                          |

**System specifications**

|                                   |                                                                                                                                          |                               |     |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|-----|
| Version                           | Screw connection, with spring-loaded cable clamp, for screwable cross-connection, for plug-in cross-connector. One end without connector | End cover plate required      | Yes |
| Number of potentials              | 1                                                                                                                                        | Number of levels              | 1   |
| No. of clamping points per level  | 2                                                                                                                                        | Number of potentials per tier | 1   |
| Levels cross-connected internally | No                                                                                                                                       | PE connection                 | No  |
| Mounting rail                     | TS 35                                                                                                                                    | N-function                    | No  |
| PE function                       | No                                                                                                                                       | PEN function                  | No  |

**Additional technical data**

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | No    | Number of similar terminals | 1       |
| Open sides               | right | Type of mounting            | Snap-on |

**CSA rating data**

|                               |                |                               |       |
|-------------------------------|----------------|-------------------------------|-------|
| Certificate No. (CSA)         | 200039-1057876 | Current size C (CSA)          | 45 A  |
| Current size D (CSA)          | 5 A            | Voltage size C (CSA)          | 300 V |
| Voltage size D (CSA)          | 600 V          | Wire cross section max. (CSA) | 8 AWG |
| Wire cross section min. (CSA) | 20 AWG         |                               |       |

**W-Series**  
**WDU 6 SL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**
**Conductors for clamping (rated connection)**

|                                                                 |                     |                                                                  |                     |
|-----------------------------------------------------------------|---------------------|------------------------------------------------------------------|---------------------|
| Blade size                                                      | 0.8 x 4.0 mm        | Clamping range, rated connection, max.                           | 6 mm <sup>2</sup>   |
| Clamping range, rated connection, min.                          | 0.5 mm <sup>2</sup> | Clamping screw                                                   | M 3.5               |
| Connection direction                                            | on side             | Gauge to IEC 60947-1                                             | A5                  |
| Number of connections                                           | 2                   | Stripping length                                                 | 16 mm               |
| Tightening torque, max.                                         | 1.6 Nm              | Tightening torque, min.                                          | 0.8 Nm              |
| Type of connection                                              | Screw connection    | Wire connection cross section, finely stranded, max.             | 6 mm <sup>2</sup>   |
| Wire connection cross section, solid core max. rated connection | 6 mm <sup>2</sup>   | Wire connection cross section, solid core, min. rated connection | 0.5 mm <sup>2</sup> |
| Wire connection cross section, stranded, rated connection, max. | 6 mm <sup>2</sup>   | Wire connection cross-section, finely stranded, min.             | 0.5 mm <sup>2</sup> |

**Rating data**

|                                 |                   |                                              |         |
|---------------------------------|-------------------|----------------------------------------------|---------|
| Rated cross-section             | 6 mm <sup>2</sup> | Rated voltage                                | 630 V   |
| Rated current                   | 41 A              | Current at maximum wires                     | 57 A    |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV              | Pollution severity                           | 2       |
| Surge voltage category          | III               |                                              |         |

**UL rating data**

|                                         |        |                                         |       |
|-----------------------------------------|--------|-----------------------------------------|-------|
| Certificate No. (UR)                    | E60693 | Conductor size Factory wiring max. (UR) | 8 AWG |
| Conductor size Factory wiring min. (UR) | 20 AWG | Conductor size Field wiring max. (UR)   | 8 AWG |
| Conductor size Field wiring min. (UR)   | 20 AWG | Current size C (UR)                     | 50 A  |
| Current size D (UR)                     | 10 A   | Voltage size C (UR)                     | 150 V |
| Voltage size D (UR)                     | 300 V  |                                         |       |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000897    | ETIM 4.0   | EC000897    |
| ETIM 5.0   | EC000897    | ETIM 6.0   | EC000897    |
| UNSPSC     | 30-21-18-11 | eClass 5.1 | 27-14-11-31 |
| eClass 6.2 | 27-14-11-90 | eClass 7.1 | 27-14-11-90 |
| eClass 8.1 | 27-14-11-20 | eClass 9.0 | 27-14-11-20 |
| eClass 9.1 | 27-14-11-20 |            |             |

**Product information**

|                                 |                                                                                                               |
|---------------------------------|---------------------------------------------------------------------------------------------------------------|
| Descriptive text ordering data  | With pollution severity degree 2, the voltage can be raised to 630 V (no increased contamination can appear). |
| Descriptive text technical data | ESI rated data: 500 V/24 A / Note the max. current of the terminal (57 A) when using the cross-connector!     |
| Descriptive text accessories    | Cross-connections, see section "W series accessories".                                                        |

**Approvals**

Approvals



ATEX



IEC EX



ROHS

Conform

### W-Series WDU 6 SL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                           |                                                    |
|---------------------------|----------------------------------------------------|
| Certificate of conformity | <a href="#">CFAT_WDU 6 SL.pdf</a>                  |
| Engineering data          | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>           |
| Operating instructions    | <a href="#">NTI_IECEX_WDU-WPE_6_SL_EN.pdf</a>      |
| Declaration of Conformity | <a href="#">DE_PT1051_20160418_813_ISSUE01.pdf</a> |

**Data sheet****W-Series  
WDU 6 SL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**W-Series**  
**WDU 6 SL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com


**Accessories**
**Test adapter**

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

| Type       | Order No.                  | Version                | GTIN (EAN)    | Qty.      |
|------------|----------------------------|------------------------|---------------|-----------|
| WTA 3 WDU4 | <a href="#">1632350000</a> | W-Series, Test adapter | 4008190209711 | 25 pc(s). |

**End plates**

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

| Type           | Order No.                  | Version              | GTIN (EAN)    | Qty.      |
|----------------|----------------------------|----------------------|---------------|-----------|
| WAP 2.5-10 SW  | <a href="#">1050010000</a> | W-Series, End plate  | 4008190406806 | 50 pc(s). |
| WAP 16+35      | <a href="#">1050100000</a> | W-Series, End plate, | 4008190079901 | 20 pc(s). |
| WTW 2.5-10     |                            | Seperation plate     |               |           |
| WAP 2.5-10 4-6 | <a href="#">1272380000</a> | W-Series, End plate  | 4050118114881 | 50 pc(s). |
| WAP 2.5-10     | <a href="#">1050000000</a> | W-Series, End plate  | 4008190103149 | 50 pc(s). |

**W-Series**  
**WDU 6 SL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com


**Accessories**
**Blank**


WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

**General ordering data**

| Type       | Order No.                  | Version                                               | GTIN (EAN)    | Qty.       |
|------------|----------------------------|-------------------------------------------------------|---------------|------------|
| WS 12/5 MC | <a href="#">1609860000</a> | WS, Terminal marker, 12 x 5 mm, Pitch in mm (P): 5.00 | 4008190203481 | 720 pc(s). |
| NE WS      |                            | Weidmueller, Allen-Bradley, White                     |               |            |

**Blank**


The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**General ordering data**


| Type       | Order No.                  | Version                                                   | GTIN (EAN)    | Qty.         |
|------------|----------------------------|-----------------------------------------------------------|---------------|--------------|
| DEK 5/5 MC | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 | 4008190397111 | 1,000 pc(s). |
| NE WS      |                            | Weidmueller, White                                        |               |              |

## W-Series WDU 6 SL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Accessories

### Hook-type cable lugs



The use of insulated connectors guarantees users a permanent and consistent quality for their electrical connections.  
 In addition, they bring advantages during installation.

#### General ordering data

| Type                | Order No.                  | Version                                                                                                       | GTIN (EAN)    | Qty.       |
|---------------------|----------------------------|---------------------------------------------------------------------------------------------------------------|---------------|------------|
| HBT 1,5 - 4,6<br>RT | <a href="#">1233340000</a> | cable lug, terminal<br>end, Insulated cable<br>connector, 0.5 mm <sup>2</sup> - 1.5<br>mm <sup>2</sup> , Red  | 4050118210972 | 100 pc(s). |
| HBT 6,0 - 4,6<br>GE | <a href="#">1216230000</a> | cable lug, terminal<br>end, Insulated cable<br>connector, 4 mm <sup>2</sup> - 6<br>mm <sup>2</sup> , Yellow   | 4050118000337 | 100 pc(s). |
| HBT 2,5 - 4,6<br>BL | <a href="#">1233330000</a> | cable lug, terminal<br>end, Insulated cable<br>connector, 1.5 mm <sup>2</sup> - 2.5<br>mm <sup>2</sup> , Blue | 4050118016901 | 100 pc(s). |

### WQV 10



#### Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

#### General ordering data

| Type      | Order No.                  | Version                                                              | GTIN (EAN)    | Qty.      |
|-----------|----------------------------|----------------------------------------------------------------------|---------------|-----------|
| WQV 10/3  | <a href="#">1054960000</a> | W-Series, Cross-connector,<br>For the terminals, No. of<br>poles: 3  | 4008190079079 | 50 pc(s). |
| WQV 10/10 | <a href="#">1052460000</a> | W-Series, Cross-connector,<br>For the terminals, No. of<br>poles: 10 | 4008190152130 | 20 pc(s). |
| WQV 10/2  | <a href="#">1052560000</a> | W-Series, Cross-connector,<br>For the terminals, No. of<br>poles: 2  | 4008190154943 | 50 pc(s). |



**W-Series  
WDU 6 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**WQV 10/4 [1055060000](#)

W-Series, Cross-connector, 4008190188245 50 pc(s).

For the terminals, No. of  
poles: 4

**End brackets****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

| Type     | Order No.                  | Version               | GTIN (EAN)    | Qty.       |
|----------|----------------------------|-----------------------|---------------|------------|
| WEW 35/2 | <a href="#">1061200000</a> | W-Series, End bracket | 4008190030230 | 100 pc(s). |

# Addresses worldwide

## Let's connect.

**AE United Arab Emirates**  
Weidmüller Middle East FZE  
Warehouse Q3-79  
SAIF-Zone  
P.O. BOX 8591  
Sharjah  
Telephone number +971 65572723  
Fax number +971 65572724  
wme.info@weidmuller.com

**AF Afghanistan**  
Representative Office  
  
AF 11050 Beograd  
Telephone number +381 11 2885 274  
Fax number +381 11 2885 274  
zoran.rabrenovic@weidmuller.com

**AO Angola**  
Please contact  
Phambili Interface  
South Africa

**AR Argentina**  
CPI SA  
Bauness 2660  
C1431DOF Buenos Aires  
Telephone number +54 11 4523 8008  
Fax number +54 11 4522 0546  
info@cpi.com.ar  
www.cpi.com.ar

**AT Austria**  
Weidmüller GmbH  
IZ NOE Süd, Str 2b, Obj M59,  
2355 Wiener Neudorf  
Telephone number +43 2236 67080  
Fax number +43 2236 6708-899  
office.at@weidmuller.com  
www.weidmuller.com

**AU Australia**  
Weidmüller Pty. Ltd.  
PO BOX 6944  
Huntingwood 2148  
Huntingwood Drive 43  
Huntingwood NSW 2148  
Telephone number +61 2 9671 9999  
Fax number +61 2 9671 9911  
info@weidmuller.com.au  
www.weidmuller.com.au

**AZ Azerbaijan**  
Representative Office  
Weidmüller Interface  
Demirchi Tower, 4th floor  
37, Khojali ave.  
AZ 1025 Baku  
Telephone number +994 12 488 80 36  
Fax number +994 12 488 80 37  
aliyar.hashimli@weidmuller.com

**BA Bosnia and Herzegovina**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia

or  
BH ES Elektrosistem d.o.o.  
Palih boraca 104  
78000 Banja Luka  
Telephone number +387 51 420 340  
Fax number  
elsist@inecco.net  
www.elektrosistem.ba  
BIG electric d.o.o  
Mladena Stojanovića 117A  
78000 Banja Luka  
Telephone number +387 51926277  
Fax number +387 51926277  
bigelectric@blic.net  
www.bigelectric.ba

**BE Belgium**  
Weidmüller Benelux B. V.  
Mechelsesteenweg 519 bus  
6 en 7  
1930 Nossegem  
Telephone number +32 2 752 40 70  
Fax number +32 2 751 36 06  
info@weidmuller.be  
www.weidmuller.be

**BG Bulgaria**  
Weid-Bul EOOD  
Bul. „Kliment Ohridski“ 13  
1756 Sofia  
Telephone number +359 2 963 2560  
Fax number +359 2 963 1098  
sofia@weidbul.com  
www.weidbul.com

**BH Bahrain**  
Khayber Trading Company  
P.O Box 1976  
Manama  
Telephone number +973 720747  
Fax number +973 720331  
khayber@batelco.com.bh

**BR Brazil**  
Weidmüller Conexel do Brasil  
Conexões Elétricas Ltda.  
Av. Presidente Juscelino, 642  
- Piraporinha  
Diadema, São Paulo  
09950-370  
Telephone number +55 (11) 4366-9600  
Fax number +55 (11) 4362-1677  
vendas@weidmuller.com.br  
www.weidmuller.com.br

**BW Botswana**  
Please contact  
Phambili Interface  
South Africa

**BY Belarus**  
TECHNIKON Ltd.  
Nezavisimosti pr. 177-9  
220125 Minsk  
Telephone number +375 17 393-11-77  
Fax number +375 17 3930080  
wm@technikon.by

**CA Canada**  
W Interconnections Canada Inc.  
10 Spy Court  
Markham Ontario L3R 5H6  
Telephone number +1 (905) 475-1507 Ext. 9836  
Fax number +1 (905) 475-2798  
support@weidmuller.ca  
www.weidmuller.ca

**CG Congo**  
Please contact  
Phambili Interface  
South Africa

**CH Switzerland**  
Weidmüller Schweiz AG  
Rundbuckstraße 2  
8212 Neuhausen am  
Rheinfall SH  
Telephone number +41 52 674 07 07  
Fax number +41 52 674 07 08  
info@weidmuller.ch  
www.weidmuller.ch

**CL Chile**  
CPI CHILE LTDA  
Av. Presidente Frei Montalva  
6001, 47 complejo el cortijo  
Santiago - Conchalí  
Telephone number +562 963 8440  
Fax number +562 963 8440  
cpi@cpichile.cl  
www.cpiichile.cl

**CN China**  
Weidmüller Interface  
(Shanghai) Co. Ltd.  
100 Yutong Road  
25 F. BM Intercontinental  
Business Center  
200070 Shanghai  
Telephone number +86 21-22195008  
Fax number +86 21-22195009  
customer.hotline@weidmuller.com.cn  
www.weidmuller.com.cn

**CO Colombia**  
Automatización Avanzada S. A.  
Carrera 97 No., 24 c - 23  
Bodega 4  
110911 Bogotá-D.C.  
Telephone number +57 (1) 547-8510  
Fax number +57 (1) 422-3044  
comercial@automatizacionavanzada.com  
www.automatizacionavanzada.com

**CR Costa Rica**  
ELVATRON S. A.  
la Uruca 400 Norte Banco  
Costa Rica  
San Jose Costa Rica  
Telephone number +506 2961-060  
Fax number +506 5200-609  
dirk.haase@elvatron.com  
www.elvatron.com

**CZ Czech Republic**  
Weidmüller s.r.o.  
Lomnického 5/1705  
140 00 Praha 4  
Telephone number +420 244 001 400  
Fax number +420 244 001 499  
office@weidmuller.cz  
www.weidmuller.cz

**DE Germany**  
Weidmüller GmbH & Co. KG  
Ohmstraße 9  
32758 Detmold  
Postfach 30 54  
32720 Detmold  
Telephone number +49 5231 1428-0  
Fax number +49 5231 14-292083  
weidmuller@weidmuller.de  
www.weidmuller.de

**DK Denmark**  
Weidmüller Danmark  
Vallensbækvej 18A  
2605 Brøndby  
Telephone number +45 27747800  
kundeservice@weidmuller.dk  
www.weidmuller.dk

**DZ Algeria**  
SARL INTER ELECTRIC  
1a Angles des Rues Okba Ibn  
Nafaa et Hassi Beida  
2300 Annaba  
Telephone number  
Fax number  
contact@inter-electric.com

**EC Ecuador**  
Elsystec S. A., Electricidad  
Sistemas y Tecnología  
Vasco de Contreras N35-251  
y Mañosca  
Quito - Pichincha  
Telephone number +593 22456510  
Fax number +593 22456755  
Elsystec@uiio.satnet.net

**EE Estonia**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Latvia  
or  
SLO Eesti AS  
11415 Tallinn  
Telephone number +372 6 272 200  
Fax number  
info@slo.ee

SLO Eesti AS  
12618 Tallinn  
Telephone number +372 622 9119  
Fax number  
elit@elit.ee  
Soots Interface OÜ  
Pärnu mnt 142  
11317 Tallinn  
Telephone number +372 609 6933  
Fax number  
info@sootsinterface.ee  
www.sootsinterface.ee

**EG Egypt**  
Standard Electric (OMEGA)  
1, Abdelhamid Badawy Street  
Heliopolis  
Cairo  
Telephone number +202 21805111  
Fax number +202 21805600  
stdelec@rite.com

**ES Spain**  
Weidmüller, S. A.  
Narcis Monturiol 11-13, Pol.  
Ind. Sudoeste  
8960 Sant Just  
Desvern - Barcelona  
Telephone number +34 934 803 386  
Fax number +34 933 718 055  
weidmuller@weidmuller.es  
www.weidmuller.es

**FI Finland**  
Weidmüller Suomi,  
Weidmüller Aktiebolagetin  
sivuliike  
Koy Plaza Vivace  
Äyritie 8C  
FI 1510 Vantaa  
Telephone number +358 20 7351300  
Fax number +358 800 114 667  
asiakaspalvelu@weidmuller.fi  
www.weidmuller.fi

**FR France**  
Weidmüller E. U. R. L.  
2 Boulevard de l'Oise  
CS 31100 CERGY  
95095 CERGY PONTOISE  
Cedex  
Telephone number +33 1 34 24 55 00  
Fax number +33 1 34 24 55 01  
mail@weidmuller.fr

**GB Great Britain**  
Weidmüller Ltd.  
Klippon House  
Centurion Court Office Park,  
Meridian East, Meridian  
Business Park  
Leicester  
LE19 1TP  
Telephone number +44 116 282 3470  
Fax number +44 116 289 3582  
marketing@weidmuller.co.uk  
www.weidmuller.co.uk

**GE Georgia**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**GH Ghana**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.

**GR Greece**  
G.A. Solutions  
Ippokratous 11 Metamorfosi  
144 52 Athen  
Telephone number +30 210 2823233  
Fax number +30 210 2823233  
info@weidmuller.gr  
www.weidmuller.gr

**GT Guatemala**  
Prestelectro, Prestegard  
Electro, S.A.  
Avenida Petapa 44-22,  
Zona 12  
Guatemala City  
Telephone number +502 2442-3346  
Fax number +502 2476-8945  
ventas@prestelectro.com

**HK Hong Kong**  
Weidmüller (Hong Kong)  
Limited Co. Ltd.  
Unit 1617, Metropolis Tower  
No. 10 Metropolis Drive,  
Hung Hom, Kowloon  
Telephone number +852 3154 8088  
Fax number +852 31548099  
Info-hk@weidmuller.com.hk

**HR Croatia**  
ElektroPARTNER d.o.o.  
Slavonska avenija 24/6  
HR-10000 Zagreb  
Telephone number +385 (1) 6184 793  
Fax number +385 (1) 6184 795  
elektropartner@zg.t-com.hr  
www.elektropartner.hr

**HU Hungary**  
Weidmüller Kereskedelmi Kft.  
Budapest  
Gubacsi út 6.  
1097  
Telephone number +36 1 382 7700  
Fax number +36 1 382 7701  
info@weidmuller.hu  
www.weidmuller.hu

**ID Indonesia**  
PT. Nego Electrindo  
Ruko Mega Grosir Cempaka  
Mas Blok I No. 20 - 22  
Jakarta 10640  
Telephone number +62 21 42882255  
Fax number +62 21 42882266  
sales@negoelectrindo.co.id

**IE Ireland**  
Please contact  
Weidmüller Ltd.  
Great Britain

**IL Israel**  
A. U. Shay Ltd.  
23/25, Embarr Street  
49222 Petach-Tikva  
P.O. Box 1 00 49  
49222 Petach-Tikva  
Telephone number +972 3-923-3601  
Fax number +972 3-923-4601  
shay@uriel-shay.com  
www.uriel-shay.com

ATEKA Ltd.  
4, Ha Tavor lane Industrial  
area Segula  
49691 Petach-Tikva  
P.O. Box 4710  
Petach-Tikva  
Telephone number +972 73-200-1311  
Fax number +972 3-924 4245  
marketing@ateka.co.il  
www.ateka.co.il



You can find all Weidmüller addresses and your local contact on the internet at: [www.weidmuller.com/countries](http://www.weidmuller.com/countries)

Let's connect.

Sales company

Representation abroad

without representation abroad

|                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>IN India</b><br>Representative Office<br>Weidmüller Electronics India Pvt. Ltd.<br>No. 9, Union Street, Off. Infantry Road<br>BANGALORE<br>560 001<br>Telephone number +91-80-22860028<br><a href="mailto:wmi@weidmuller.in">wmi@weidmuller.in</a><br><a href="http://www.weidmuller.com">www.weidmuller.com</a>                    | <b>KW Kuwait</b><br>Kana Controls General Trading & Contracting Co. W. L. L.<br>Al Rai Industrial Area, Plot 28-30, St. 31<br>13016 Safat<br>B.P. 25593<br>Telephone number +965 4741373<br>Fax number +965 4741537<br><a href="mailto:info@kanacontrols.com">info@kanacontrols.com</a><br><br>Petroleum Services Co. W.L.L.<br>Kuwait Trade Free Zone Area P.O. Box 4098 Safat 13041<br><br>Telephone number +96524610801/2/3 ext. 208 II<br>Fax number +96524613754<br><a href="mailto:psc-systems@petserv.net">psc-systems@petserv.net</a> | <b>MD Moldova</b><br>Inoxpa Solutions SRL<br>20, Igor Vieru street<br>MD-2075 Chisinau<br>Moldova<br>Telephone number +373 (22) 866665<br>Fax number +373 (22) 866663<br><a href="mailto:atiuleanu@gmp-moldova.com">atiuleanu@gmp-moldova.com</a><br><a href="http://www.gmp-moldova.com">www.gmp-moldova.com</a>                          | <b>NA Namibia</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | <b>PK Pakistan</b><br>Automation Controls (Pak) Apartment No. 33 C III, Chensab Block, Allama Iqbal Town<br>Lahore<br>Telephone number +92 42 37809948<br>Fax number +92 42 37809950<br><a href="mailto:nadeem@acpak.com.pk">nadeem@acpak.com.pk</a><br><a href="http://www.acpak.com.pk">www.acpak.com.pk</a>                                                                                                                                                                                                                           |
| <b>IR Iran</b><br>Representative Office<br>Tamin Ehtiajat Fanni Tehran (TAF Co.)<br>No. 36, West 4th St., Ettehad Ave. Damavand Rd.<br>Tehran - 1658674583, Iran<br>Telephone number +9821 77120809<br><a href="mailto:info@taf-co.com">info@taf-co.com</a><br><a href="http://www.taf-co.com">http://www.taf-co.com</a>               | <b>KZ Kazakhstan</b><br>Please contact<br>Weidmüller Group<br>Russia                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | <b>ME Montenegro</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Serbia.                                                                                                                                                                                                                       | <b>NG Nigeria</b><br>Please contact<br>Weidmüller Interface GmbH & Co. KG<br>South Africa                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | <b>PL Poland</b><br>Weidmüller Sp. z o. o.<br>ul. Ogrodowa 58<br>00-876 Warszawa<br>Telephone number +48 22 510 09 40<br>Fax number +48 22 510 09 41<br><a href="mailto:biuro@weidmuller.com.pl">biuro@weidmuller.com.pl</a><br><a href="http://www.weidmuller.pl">www.weidmuller.pl</a>                                                                                                                                                                                                                                                 |
| <b>IS Iceland</b><br>Samey Automation Center<br>Lyngas 13<br>210 Garoabaer<br>Telephone number +354 510 5200<br>Fax number +354 5 10 5201<br><a href="mailto:Samey@samey.is">Samey@samey.is</a><br><a href="http://www.samey.is">www.samey.is</a>                                                                                      | <b>LB Lebanon</b><br>Progress Engineering & Trading Enterprises<br>Al Nahr Street<br>Beirut 11-1111<br>Telephone number +961 1 444 664<br>Fax number +961 1 561 880<br><a href="mailto:progress@inco.com.lb">progress@inco.com.lb</a>                                                                                                                                                                                                                                                                                                         | <b>MG Madagascar</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                                                                               | <b>NL Netherlands</b><br>Weidmüller Benelux B. V.<br>Franciscusweg 221<br>1216 SE Hilversum<br>P.O. Box 1505<br>1200 BM Hilversum<br>Telephone number +31 35 626 12 61<br>Fax number +31 35 623 20 44<br><a href="mailto:info@weidmuller.nl">info@weidmuller.nl</a><br><a href="http://www.weidmuller.nl">www.weidmuller.nl</a>                                                                                                                                                                                                                                                   | <b>PR Puerto Rico</b><br>Please contact<br>W Interconnections Inc.<br>United States                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <b>IT Italy</b><br>Weidmüller S. r.l.<br>Via Albert Einstein 4<br>20092 Cinisello Balsamo Milano<br>Telephone number +39 02 680681<br>Fax number +39 02 6124945<br><a href="mailto:weidmuller@weidmuller.it">weidmuller@weidmuller.it</a><br><a href="http://www.weidmuller.it">www.weidmuller.it</a>                                  | <b>LT Lithuania</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Latvia<br><br>or<br>ELEKTROS IRANGA<br>Tinklų g. 29 a<br>LT-5319 Panevezys<br>Telephone number +370 (45) 582 828<br>Fax number +370 (45) 582 727<br><a href="mailto:info@eliranga.lt">info@eliranga.lt</a><br><br>UAB „SLO Lithuania“<br>Vilkipėdės g. 4<br>LT-LT-03151 Vilnius<br>Telephone number +370 5 215 00 70<br>Fax number +370 5 215 00 71<br><a href="mailto:biuras@slo.lt">biuras@slo.lt</a>                           | <b>MK Macedonia</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Serbia<br><br>or<br>ELEKTRO - SMK dooel<br>UL. III Makedonska brigada b.b.<br>1000 Skopje<br>Telephone number +389 22460295<br>Fax number<br><a href="mailto:Elektro-smk@telekabel.net.mk">Elektro-smk@telekabel.net.mk</a>    | <b>NO Norway</b><br>Sivilingeniør J.F. Knudtzen AS<br>Billingstadsletta 97<br>1396 Billingstad<br>PO Box 160<br>1378 Nesbru<br>Telephone number +47 66 98 33 50<br>Fax number +47 66 98 09 55<br><a href="mailto:firmapost@jfkudtzen.no">firmapost@jfkudtzen.no</a><br><a href="http://www.jfkudtzen.no">www.jfkudtzen.no</a>                                                                                                                                                                                                                                                     | <b>PT Portugal</b><br>Weidmüller Sistemas de Interface S. A.<br>Estrada Outeiro Polima, R. Augusto Dias da Silva, Lote B - Esc. 2<br>São Domingos de Rana 2785-515 Abóboda<br>Telephone number +351 214 459 191<br>Fax number +351 214 455 871<br><a href="mailto:weidmuller@weidmuller.pt">weidmuller@weidmuller.pt</a><br><a href="http://www.weidmuller.pt">www.weidmuller.pt</a>                                                                                                                                                     |
| <b>JM Jamaica</b><br>Please contact<br>W Interconnections Inc.<br>United States                                                                                                                                                                                                                                                        | <b>LU Luxembourg</b><br>Please contact<br>Weidmüller Benelux B. V.<br>Netherlands                                                                                                                                                                                                                                                                                                                                                                                                                                                             | <b>MT Malta</b><br>E. S. S., Electrical Supplies & Services Ltd.<br>San Gwakkim Road<br>Mriehel<br><br>Telephone number +356 21255777<br>Fax number +356 21255999<br><a href="mailto:robert.agius@ess.com.mt">robert.agius@ess.com.mt</a>                                                                                                  | <b>NZ New Zealand</b><br>Cuthbert S. Steward Ltd.<br>27 Te Puni Street<br>Petone<br>PO Box 38496<br>Wellington Mail Centre 5054<br>Telephone number (04) 568 6156<br>Fax number (09) 489 1752<br><a href="mailto:csi@cuthbertstewart.co.nz">csi@cuthbertstewart.co.nz</a><br><br>Cuthbert S. Steward Ltd<br>4 Fred Thomas Drive<br>Aon Building, Ground Floor,<br>South Entry<br>Takapuna<br>PO Box 100 338<br>North Shore City 745<br>Telephone number (09) 489 1751<br>Fax number (04) 568 6056<br><a href="mailto:csiak@cuthbertstewart.co.nz">csiak@cuthbertstewart.co.nz</a> | <b>PY Paraguay</b><br>Please contact<br>CPI SA<br>Argentina                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| <b>JO Jordan</b><br>Billeh Electricals Mat. Co.<br>PO Box 4343<br>Amman<br>Telephone number +962 6 4656 987<br>Fax number +962 6 4649 216                                                                                                                                                                                              | <b>LV Latvia</b><br>SIA Abi4<br>Daugavgrivas 49 k3<br>Riga, LV-1007<br>Telephone number +371 674 70999<br>Fax number<br><a href="mailto:abi_4@tvnet.lv">abi_4@tvnet.lv</a><br><br>Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Udens str. 12-118<br>Riga, LV-1007<br>Telephone number +371 29254766<br>Fax number<br><a href="mailto:lgonis.rudaks@weidmuller.com">lgonis.rudaks@weidmuller.com</a><br><a href="http://www.weidmuller.com">www.weidmuller.com</a>                                                           | <b>MU Mauritius</b><br>Mubelo Electrical Ltd.<br>Office 26, Gateway building,<br>St Jean Road<br>Quatre Bornes<br>Mauritius<br>Telephone number +230 4670989<br>Fax number +230 4654051<br><a href="mailto:richard.mubelo@orange.mu">richard.mubelo@orange.mu</a>                                                                          | <b>OM Oman</b><br>DAN INTERNATIONAL LLC.<br>Ghala St. 111<br>BP 2901<br>Seeb<br>Telephone number +968 5036 77<br>Fax number +968 5037 55<br><a href="mailto:yedu@danintl.com">yedu@danintl.com</a>                                                                                                                                                                                                                                                                                                                                                                                | <b>QA Qatar</b><br>Doha Motors<br>PO Box 145<br><br>Telephone number +974 4651441<br>Fax number +974 4654579<br><a href="mailto:dmtctech@qatar.net.qa">dmtctech@qatar.net.qa</a><br><a href="http://www.dohamotorsgroup.com/td.html">http://www.dohamotorsgroup.com/td.html</a>                                                                                                                                                                                                                                                          |
| <b>JP Japan</b><br>Nihon Weidmüller Co. Ltd.<br>Sphere Tower Tennoz 2-2-8 Higashi-Shinagawa, Shinagawa-ku<br>Tokyo<br>140-0002<br>Telephone number +81 3 6711 5300<br>Fax number +81 3 6711 5333<br><a href="mailto:info@weidmuller.co.jp">info@weidmuller.co.jp</a><br><a href="http://www.weidmuller.co.jp">www.weidmuller.co.jp</a> | <b>RO Romania</b><br>Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Ionescu Crum Street, No. 1, 1st Tower, 1st Floor, Office 4<br>500446 Brasov - Brasov Business Park<br>Telephone number +40 (268) 446 222<br>Fax number +40 (268) 446 224<br><a href="mailto:claudiu.totea@weidmuller.com">claudiu.totea@weidmuller.com</a><br><a href="http://www.weidmuller.ro">www.weidmuller.ro</a>                                                                                                                                    | <b>MX Mexico</b><br>W Interconnections S. A.<br>DE C. V.<br>Bldv. Hermanos Serdán 698, Col. San Rafael Oriente 72029 Puebla<br>Telephone number +52 (222) 268 6227<br>Fax number +52 (222) 286 6242<br><a href="mailto:clientes@weidmuller.com.mx">clientes@weidmuller.com.mx</a>                                                          | <b>PE Peru</b><br>IMPEXINCA S.A.C.<br>Calle Ortiz de Zevallos No. 105, Urb. San Antonio 18<br>Lima, Miraflores<br>Telephone number +51 1 447 5608<br><a href="mailto:info@impexinca.pe">info@impexinca.pe</a><br><a href="http://www.impexinca.pe">www.impexinca.pe</a><br><br>J & W CIA. S. A.<br>Calle 6 Mz. D Lte. 23, Urb. Ind. Grimanesa 01<br>Callao<br>Telephone number +51 1 572 2539<br>Fax number +51 1 572 0152<br><a href="mailto:contacto@jwcia.com">contacto@jwcia.com</a><br><a href="http://www.jwcia.com">www.jwcia.com</a>                                      | <b>RS Serbia</b><br>Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>Ustanicka 189, III sprat lokal 7a<br>11050 Beograd<br>Telephone number +381 112885274<br>Fax number +381 112885274<br><a href="mailto:zoran.rabrenovic@weidmuller.com">zoran.rabrenovic@weidmuller.com</a><br><br>TeLa Elektrik d.o.o.<br>Ul. Dr. Drage Ljocić 6<br>Beograd<br>Telephone number +381 11 2772 415<br>Fax number +381 11 2772 850<br><a href="mailto:office@tela.rs">office@tela.rs</a><br><a href="http://www.tela.rs">www.tela.rs</a> |
| <b>KE Kenya</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface GmbH & Co. KG<br>South Africa.                                                                                                                                                                                                                  | <b>MA Morocco</b><br>Sofimed<br>137, Bd Moulay Ismail Roches Noires<br>20290 Casablanca<br>Telephone number<br>Fax number<br><a href="mailto:contact@sofimedmaroc.com">contact@sofimedmaroc.com</a>                                                                                                                                                                                                                                                                                                                                           | <b>MY Malaysia</b><br>Connect Plus Technology Sdn Bhd<br>No. 43, Jalan PJS 11/22, Bandar Sunway<br>46150 Petaling Jaya<br>Selangor Darul Ehsan<br>Telephone number +60 3 5633 7363<br>Fax number +60 3 5633 6562<br><a href="mailto:paul@cptech.com.my">paul@cptech.com.my</a><br><a href="http://www.cptech.com.my">www.cptech.com.my</a> | <b>PH Philippines</b><br>Enclosure Systems Specialists Inc.<br>2276 Don Chino Roces Avenue Extension<br>Room 103/105 Narra Building<br>1231 Makati City<br>Telephone number +63 2 813 8580<br>Fax number +63 2 813 8596<br><a href="mailto:sales_encsys@pltdsl.net">sales_encsys@pltdsl.net</a><br><a href="http://www.enclosuresystemsph.com">www.enclosuresystemsph.com</a>                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>KG Kyrgyzstan</b><br>Please contact<br>our Representative Office<br>Weidmüller Interface<br>Azerbaijan.                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | <b>MZ Mozambique</b><br>Please contact<br>Phambili Interface<br>South Africa                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>KR Korea</b><br>Weidmüller Korea Co. Ltd.<br>9th floor<br>429, Teheran-ro, Gangnam-Gu<br>Seoul 135-721<br>Telephone number +82 2-516-0003<br>Fax number +82 2-516-0090<br><a href="mailto:info@weidmuller.co.kr">info@weidmuller.co.kr</a><br><a href="http://www.weidmuller.co.kr">www.weidmuller.co.kr</a>                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |

# Addresses worldwide

Let's connect.

- RU Russia**  
Weidmüller Group  
7/10 Khlebozavodskiy  
Passage,  
Moskau  
115230  
Telephone number +7 495  
280 72 71  
Fax number +7 495 280  
72 71  
Info@weidmueller.ru  
www.weidmueller.ru
- SA Saudi Arabia**  
Al Abdulkarim Holding Co.  
P.O. Box 4  
Dammam 31411  
Telephone number +966 3  
8337 110  
Fax number +966 3  
8829547  
E-mail salehsk@akh.com.sa  
www.weidmueller.ae  
  
Saudi Electric Supply  
Company (SESCO)  
P.O. Box 32 98  
Al Khobar 31952  
Telephone number +966 3  
8829546 Ext. 3030  
Fax number  
E-mail Safdar.Malik@sescogex.com  
www.sesco-gex.com
- SE Sweden**  
Weidmüller AB  
Axel Danielssons väg 271  
BOX 31025  
SE-200 49 Malmö  
Telephone number +46 77-  
143 00 44  
Fax number +46 40-37 48 60  
info@weidmuller.se  
www.weidmuller.se
- SG Singapore**  
Weidmüller Pte. Ltd.  
70 Bendemeer Road  
# 04-03 Luzerne Building  
Singapore 339940  
Telephone number +65 6841  
5311  
Fax number +65 6841 5377  
info@weidmuller.com.sg  
www.weidmuller.com.sg
- SI Slovenia**  
Elektrospoji d. o. o.  
Stegne 27  
Sl- 1000 Ljubljana  
Osrednjeslovenska  
Telephone number +386 1  
511 3810  
Fax number +386 1 511  
1604  
info@elektrospoji.si  
www.elektrospoji.si
- SK Slovakia**  
ELEKTRIS s.r.o.  
Elektrárenská 1  
831 04 Bratislava  
Telephone number +421  
2/4920 0113  
Fax number +421 2/4920  
0119  
bratislava@elektris.sk
- SV El Salvador**  
Prestegard Electro  
11 Avenida Norte No. 240  
Edificio Salazar No. 2  
San Salvador  
Telephone number +503  
2271 1690  
Fax number +503 2221  
3851  
prestegard@navegante.com.sv
- SY Syria**  
Please contact  
Weidmuller Middle East FZE  
United Arab Emirates
- SZ Swaziland**  
Please contact  
Phambili Interface  
South Africa
- TH Thailand**  
Pisanu Engineering Co. Ltd.  
Kwang Dingaeng, Khet  
Dingaeng  
800/2 Soi Trakulsuk, Asoke-  
dindaeng Road  
Dindaeng, Bangkok  
10400  
Telephone number +66 2  
248 2896  
Fax number +662 105 6301  
ecsales@pisanu.co.th  
www.pisanu.co.th  
  
Representative Office  
Weidmüller Pte. Ltd.  
37/F, Sathorn Square Building  
98 North Sathorn Road  
Bangkok, Silom Bangrak  
10500  
Telephone number +66 2  
105 6300  
Fax number +66 2 642 9220  
info@weidmuller.com.sg
- TJ Tajikistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- TM Turkmenistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- TN Tunisia**  
Please contact  
Weidmüller E. U. R. L.  
France
- TR Turkey**  
Weidmüller Elektronik Ticaret  
Ltd. Sirketi  
Kavacik Mah. Orhan Veli Kanik  
Caddesi 9/1  
34810 Beykoz / Istanbul  
Telephone number +90 (216)  
537 10 70  
Fax number +90 (216) 537  
10 77  
info@weidmuller.com.tr  
www.weidmuller.com.tr
- TW Taiwan**  
Please contact  
Weidmuller (Hong Kong)  
Limited Co. Ltd.  
Hong Kong
- TZ Tanzania**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.
- UA Ukraine**  
LLC WM UKRAINE  
Levanevskogo str. 6  
Kiev  
3058  
Telephone number +38 044  
490 32 48  
Fax number  
info@wm-ua.com.ua  
wm-ua.com.ua/  
  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Z, office 303  
7-D, Zdolbunivska str.  
Kiev, 2081  
Telephone number  
(mobile) +38 050 440 25 24  
info.ua@weidmueller.com
- US United States**  
W Interconnections Inc.  
821 Southlake Boulevard  
Richmond Virginia 23236  
Telephone number +1 (804)  
794-2877  
Fax number +1 (804) 379-  
2593  
info@weidmuller.com  
www.weidmuller.com
- UY Uruguay**  
REWO Uruguay S. A.  
AV. Bolivia 2001Esq  
Roca fuerte  
11300 Carrasco Montevideo  
Telephone number +598  
2604 8439  
Fax number +598 2604  
8439  
rewo@rewouruguay.com.uy
- UZ Republic of Uzbekistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.
- VE Venezuela**  
Somerinca C. A.  
Corazon de Jesus - 3ra  
Transversal con calle el  
Carmen- Los Dos Caminos  
Caracas 1070-A  
Telephone number +58  
2122352748  
Fax number +58  
2122399341  
klocmoeller@cantv.net  
www.somerinca.com
- VN Vietnam**  
AUMI Industrial Equipment &  
Automation Company Limited  
E1, La Thanh Hotel  
218 Doi Can Street  
Lieu Giai Ward, Ba Dinh  
District  
Hanoi City  
Telephone number +84 4  
37628601  
Fax number +84 4  
62661391  
aumi@aumi.com.vn  
www.aumi.com.vn  
  
Representative Office  
Weidmüller Pte. Ltd.  
Level 16 Saigon Tower  
Building  
29 Le Duan Street  
District 1  
Ho Chi Minh  
Telephone number +848  
3520 7717  
Fax number +848 3520  
7604  
info@weidmuller.com.sg
- ZA South Africa**  
Phambili Interface  
PO Box 193  
1609 Johannesburg, Edenvale  
5 Bundo Road, Sebenza  
1610 Johannesburg  
Telephone number +27 (11)  
4521930  
Fax number  
info@weidmuller.co.za  
www.weidmuller.co.za  
  
Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
210 Amarand  
Avenue, Pegasus Building  
181 Pretoria, waterkloof Glen  
ext 2 -  
Telephone number +27 12  
003 2906  
Fax number +27 (11)  
4526455  
Jacques.Vosloo@weidmueller.  
com  
www.weidmueller.com
- ZM Zambia**  
Please contact  
Phambili Interface  
South Africa
- ZW Zimbabwe**  
Please contact  
Phambili Interface  
South Africa