UNIVERSAL PROGRAMMER ZIF48 SOCKET EXPANDABLE TO TO 144 PINS
USB2.0 PORT OR STAND-ALONE MODE
FOR PROMs, EPROMs, EEPROMs, FLASHs, PLDs, MICROCONTROLLERS

Support over 98.000 devices

Introduction:

The SuperPro-6100 is an universal programmer equipped with ARM7 processor in USB-2. Thanks to its ZIF48 socket it can program over 98.000 different components among EPROMs, EEPROMs, FLASHs memories, PLDs and microcontrollers. Over, it can program components, as BGA package, until 144 programmable pins drivers thanks to its interchangeable socket. A LCD display screen of 20 x 2 characters as well as a keypad allow to use this programmer in stand-alone mode. This mode enables it, thanks to the addition of an optional classical compact Flash card (512Mb or 1Gb) inserted in the back of the programmer, to download numerous algorithms in the SuperPro-6100. Therefore, this allows it to operate without a computer in cases when you need to use it away from the office, or just when you want to use the SuperPro-6100 as a production programmer to make copies very quickly with the automatic detection of a device's presence to start programming (5 times faster than when it is connected to a PC). It can program low-voltage components until 1,2V. It does not need any adapters for all components in SDIP package. The programming is extremely fast thanks to the use of algorithm technology downloaded in the CPU of the programmer during the selection of a device. The SuperPro-6100 can also test the pins of the inserted device to detect possible faults : incorrect insertion of the device, defective pin...etc. It is also protected against shorts and overvoltage. An optional ISP adapter permits to program components soldered on printed circuits or devices in special packages. The software works with Windows 98/ME/NT/2000/XP/Windows7/Windows8/ Windows10 (32/64 bits). It allows advanced production functions such as automatic programming as soon as the device is detected, verification of the device ID and automatic generation of serial numbers in the device. Software updates are free.

Features:

Accepts standard file formats: JEDEC, INTEL (Extended) HEX, HOLTEK, EMC(.CDS), INTEL HEX16, Motorola S record, BINARY, Tektronix (linear & segmented), and auto find format.
Manages 16 and 32 bit word split (Set Programming).
Automaticly identifies the manufacturer and type of E(E)PROMs, auto identifies TTL/CMOS logic IC.
Device insertion test and poor pin contact check.
Universal DIP, PLCC, QFP, TSOP, PSOP, SOIC, SSOP, SDIP adapters, (support from 6 pin to 300 pin device packages).
Auto-run mode starts programming automatically upon detection of chip insertion.
Supports Windows XP / VISTA / Windows 7 / Windows 8.1 / Windows10 (32bits and 64bits) with 100MB of spare capacity.

Hardware & Electrical specifications:

Dimensions product : 145 x 210 x 95mm. Weight : 1600g
Dimensions packaging : 310 x 260 x 150mm. Weight : 2800g
Power supply : adapter with AC input 85V to 260V, 50Hz/60Hz, output 12Vdc.
Interface : connect to laptop or PC throught USB port (USB 2.0 high speed)
Support : ZIF48 universal pin-drivers, (support 8 pins to 48 pins DIP package).

Item includes:

- Programmer with 48 pins ZIF socket include.
- Power pack 85-260Vac / 12Vdc.
- USB-B to USB-A cable.
- Software on CD.
- User manual in English and French.

Products informations : www.seeit.fr

Options :

ISP-HEADER01 : ICSP adapter.
Universal adapters PLCC, SO, QFP,...

Devices list programmed below

DEVICES LIST SUPERPRO-6100
(Universal stand alone programmer with 144 pins drivers)

Push "CTRL + F" keys to find a component

Universal programmer SuperPro-6100

Total manufacturers : 364
Total devices : 98169
Revision 1652

```
Explanation to read a device:
Example:  24LC16B@SOIC8 [CX1045]
24LC16B:  Device name
@SOIC8:   Package name
[CX1045]: Adapter name (if needed)
```

Manufacturers:

ABOV	ACE	ACE Technology	ACT
ACTIVE-SEMI	ACTRANS	ADESTO	ADI
ADVANCE GROUP	AEROFLEX	AIROHA	
AiT Semiconductor		ALI(Acer)	ALL24SERIES
ALLFLASH	ALLIANCE	ALTCO	ALTERA
AMD	AMIC	AMS	ANACHIP
APLUS FLASH	ARTSCHIP	ASAHI KASEI(AKM)	ASD
ASI	Asic Microelectronics		ASP
ASTIGP-MICROCHIP	ATC	ATMEL	ATMEL W&M
ATMEL-CUSTOM	ATMEL-CUSTOMER	ATO	AUO
AUSTIN	AUX	AXELITE	AZOTEQ
BB	BEKEN	BELLING	BENCHMARQ
BERGMICRO	BILWAY	BJX	BMT
BOCH	Bookly Micro	BRIGHT	CATALYST
CBC Microelectronics		CERAMATE	CETC58
CFEON	CHEMTRONICS	CHIGO	CHINA CORE
CHINGIS	CHIPCON	CHIPMAST	CHIPON
CHIPONE	CHIPSEA	CHIPSIP	CHIPSWINNER
CHK	CHRONTEL	CKD Technology	CORERIVER
Customer	CW	CWI	CYGNAL
CYPRESS	CYROD	DALLAS	DENSE-PAC
DEUTRON	DYCMCU	EASTSOFT	ECHELON
E-CMOS	EETI	EFST	eGalax
ELECTRONIC ARRAYS		ELPIDA	EM
EMTC	ENERGY	EON	EON-CUSTOMER
EOREX	EPSON	ESIGMA	ESMT
ESMT-CUSTOMER	ESTEK	E-TRAND	EVERSPIN
EVERSTAR	EXAR	EXCELSEMI	EXEL
EXPLORE	FAIRCHILD	FDI	FIDELIX
FIRST-RANK Technology		FLEXTRONICS	FOCALTECH
FORCE TECHNOLOGIES		FORCREAT	FORWARD

FREESCALE	Fremont Micro Devices		FTDICHIP
FUDAN	FUJITSU	FULLRICH	GAMMA
GATELEVEL	GENCORE	GENERAL(GI)	GENERALPLUS
GENERIC	GENITOP	GENUSION	GIANTEC
GIGADEVICE	GMT	GOAL	GOODIX
GOULD	GREEN-ENGINE	GREENLIANT	GREENWICH
GSI	GTM	HAIER	HARRIS
HIKVISION	HIMAX	HITACHI	HITRENDTECH
HODGEN	HOLTEK	HONEYWELL	HONGKONG
HOPEFIND	HUAJIE Technology		HUAWEI
HYNITRON	HYNIX	HYNIX(HYUNDAI)	HYNIX-CUSTOMER
HYUNDAI	IC Microsystems	ICE	ICMIC
ICSI	ICT	IDT	IGS
IK Semiconductor	ILITEK	IML	IMT
INFINEON	INTEGRAL	INTEL	INTELSIL
INTERSIL	Intretech	IR	ISGAL
ISSI	JSC	KINGSTON	K-LINE
KODENSHI	LATTICE	LEAHKIINN	LEAHKINN
LG	LG Semicon	LGEPARTNER	lierda
LINEAR	LINKSMART	LITAO	LIZE
LUMINARY	LYONTEK	MACRONIX	MAGNACHIP
MAXCOM	MAXIM	MAXWELL	MEGAWIN
MEMC	MEMOCOM	MICON	MICROCHIP
MICROCHIP(SST)	MICRON	MICRONAS	MICRON-CUSTOMER
MICROSEMI	MIP	MIRA	MIRA-CUSTOMER
MITSUBISH	MITSUBISHI	MOSEL-VITELIC	MOSMIC
MOSTEK	MOTOROLA	MShine	MT
MXIC	MXIC-CUSTOMER	MY-MS	MYSON
NAMUGA	NANOIC	NANSI	NANTRONICS
NANYA	NATRONICS	NEC	NEXFLASH
NJRC	NORDIC	NOVATEK	NSC
NTE	NUMONYX	NUVOTON	NXP
OKI	ON	ON Semiconductor	On-Bright
PANASONIC	PARAGON	PARALLAX	PCT
PHILIPS	PJ	PMC	PORTEK
POWERFLASH	POWER-RAIL	PSS	PTC
QISDA-CUSTOMER	QIXIN	QP semiconductor	Quick Pulse
RAMTRON	RATO	RAYDIUM	REALTEK
RENESAS	RICHTEK	RICOH	ROCKWELL
ROHM	SAIFUN	SAMSUNG	SAMSUNG-CUSTOMER
SANDISK	SANDISK-CUSTOMER	SANYO	SCENIX
SEEQ	SEIKO	SGS-THOMSON	SHARP
SHENHUI	SIEMENS	SIERRA	SIGNETICS
Silan	SILICON	Silicon Laboratories	
SILICON7	SIMTEK	SINOWEALTH	SIRF
SMI	SMOS	SMSC	SONIX
SONY	SPACE ELECTRONICS[SEi]		SPANSION
SPANSION-CUSTOME	SPANSION-CUSTOMER		SSSC

SST	SST-CUSTOMER	SSU	ST
STC	ST-CUSTOMER	SULC	SUMMIT
SUMSUNG	SUNMOON	SUNPLUS	SYNAPTICS
SYNCMOS	SYNERTEK	SYNTEK	SZXG
TDICOMS	TECHALL	TECHCODE	TEKMOS
TELFORD	TEMIC	TERIDIAN	
Terra Semiconductor		TI	TI-CUSTOMER
TMC	TOPRO	TOPSCOMM	TOSHIBA
TOSHIBA-CUSTOMER	TURBO IC	UBICOM	UMC
UNIGEN	VANTIS	VERSACHIPS	VLSI
WELTREND	WHITE ELECTRONIC DESIGNS		WINBOND
WING Shing	WSI	XELTEK	XICOR
XILINX	XINNOVA	XINYANG	XUMARS
YMC	YSS	YXLDZ	ZENTEL
ZENTEL-CUSTOMER	ZETTA	ZHENGXIN	ZHIXIN
ZILOG	ZMD	ZOWEE	

Devices list :

ABOV

MICROCONTROLLER

GMS34004TK [DX0001]	GMS34004TM [DX0001]
GMS34004TW [DX0001]	GMS34112TK [DX0001]
GMS34112TK@SOIC20 [DX1033]	GMS34112TK@SSOP20 [DX1026]
GMS34140TK [DX0001]	GMS34140TK@SOIC24 [DX1033]
GMS80C701 [DX0001]	GMS80C701@PLCC44 [DX2044]
GMS80C701@TQFP44 [DX3002]	GMS81004(dip20) [DX0001]
GMS81004(dip24) [DX0001]	GMS81004(dip28) [DX0001]
GMS81004@PLCC44 [DX2044]	GMS81004@SOIC20 [DX1033]
GMS81004@SOIC24 [DX1033]	GMS81004@SOIC28 [DX1033]
GMS81008(dip20) [DX0001]	GMS81008(dip24) [DX0001]
GMS81008(dip28) [DX0001]	GMS81008@PLCC44 [DX2044]
GMS81008@SOIC20 [DX1033]	GMS81008@SOIC24 [DX1033]
GMS81008@SOIC28 [DX1033]	GMS81016(dip20) [DX0001]
GMS81016(dip24) [DX0001]	GMS81016(dip28) [DX0001]
GMS81016@PLCC44 [DX2044]	GMS81016@SOIC20 [DX1033]
GMS81016@SOIC24 [DX1033]	GMS81016@SOIC28 [DX1033]
GMS81024(dip20) [DX0001]	GMS81024(dip24) [DX0001]
GMS81024(dip28) [DX0001]	GMS81024@PLCC44 [DX2044]
GMS81024@SOIC20 [DX1033]	GMS81024@SOIC24 [DX1033]
GMS81024@SOIC28 [DX1033]	GMS81032(dip20) [DX0001]
GMS81032(dip24) [DX0001]	GMS81032(dip28) [DX0001]
GMS81032@PLCC44 [DX2044]	GMS81032@SOIC20 [DX1033]
GMS81032@SOIC24 [DX1033]	GMS81032@SOIC28 [DX1033]
GMS81504AT [DX0032]	GMS81504T [DX0032]
GMS81516 [DX0001]	GMS81516@LQFP64 [DX3011]

GMS81516@MQFP64 [DX3015]
GMS81516@SDIP64 [DX0064]
GMS81516AT [DX0001]
GMS81516AT@LQFP64 [DX3011]
GMS81516AT@MQFP64 [DX3015]
GMS81516AT@SDIP64 [DX0064]
GMS81516BT [DX0001]
GMS81516BT@LQFP64 [DX3011]
GMS81516BT@MQFP64 [DX3015]
GMS81516BT@SDIP64 [DX0064]
GMS81524 [DX0001]
GMS81524@LQFP64 [DX3011]
GMS81524@MQFP64 [DX3015]
GMS81524@SDIP64 [DX0064]
GMS81524AT [DX0001]
GMS81524AT@LQFP64 [DX3011]
GMS81524AT@MQFP64 [DX3015]
GMS81524AT@SDIP64 [DX0064]
GMS81524BT [DX0001]
GMS81524BT@LQFP64 [DX3011]
GMS81524BT@MQFP64 [DX3015]
GMS81524BT@SDIP64 [DX0064]
GMS81604T [DX0001]
GMS81604T@PLCC44 [DX2044]
GMS81604T@SDIP42 [DX0042]
GMS81608T [DX0001]
GMS81608T@PLCC44 [DX2044]
GMS81608T@SDIP42 [DX0042]
GMS81C5016(dip28) [DX0001]
GMS81C5016(dip40) [DX0001]
GMS81C5016@PLCC44 [DX2044]
GMS81C5016@SOIC28 [DX1033]
GMS81C5016@TQFP44 [DX3002]
GMS81C5024(dip28) [DX0001]
GMS81C5024(dip40) [DX0001]
GMS81C5024@PLCC44 [DX2044]
GMS81C5024@SOIC28 [DX1033]
GMS81C5024@TQFP44 [DX3002]
GMS81C5032(dip28) [DX0001]
GMS81C5032(dip40) [DX0001]
GMS81C5032@PLCC44 [DX2044]
GMS81C5032@SOIC28 [DX1033]
GMS81C5032@TQFP44 [DX3002]
GMS82516T [DX0001]
GMS82516T@LQFP64 [DX3011]
GMS82516T@MQFP44 [DX3002]
GMS82516T@MQFP64 [DX3015]
GMS82516T@SDIP42 [DX0042]
GMS82516T@SDIP64 [DX0064]
GMS82524T [DX0001]
GMS82524T@LQFP64 [DX3011]
GMS82524T@MQFP44 [DX3002]
GMS82524T@MQFP64 [DX3015]
GMS82524T@SDIP42 [DX0042]
GMS82524T@SDIP64 [DX0064]
GMS84512T@SDIP52 [DX0056]
GMS84524T@SDIP52 [DX0056]
GMS87C1102 [DX0001]
GMS87C1102@SOP16 [DX1033]
GMS87C1202 [DX0001]
GMS87C1202@SOP20 [DX1033]
GMS87C1404 [DX0001]
GMS87C1404@SOP28 [DX1033]
GMS87C1408 [DX0001]
GMS87C1408@SOP28 [DX1033]
GMS87C2020@LQFP64 [DX3011]
GMS87C2020@MQFP64 [DX3015]
GMS87C2020@SDIP64 [DX0064]
GMS87C5032(dip28) [DX0001]
GMS87C5032(dip40) [DX0001]
GMS87C5032@PLCC44 [DX2044]
GMS87C5032@SOIC28 [DX1033]
GMS87C5032@TQFP44 [DX3002]
GMS87C5108@PQFP80 [DX3019]
GMS87C7008@LQFP64 [DX3011]
GMS87C7008@MQFP64 [DX3015]
GMS87C7008@SDIP64 [DX0064]
GMS87C7016@LQFP64 [DX3011]
GMS87C7016@MQFP64 [DX3015]
GMS87C7016@SDIP64 [DX0064]
GMS97C1051 [DX0001]
GMS97C1051@SOIC20 [DX1033]
GMS97C2051 [DX0001]
GMS97C2051@SOIC20 [DX1033]
GMS97C51 [DX0001]
GMS97C51@PLCC44 [DX2044]
GMS97C51@TQFP44 [DX3002]
GMS97C51H [DX0001]
GMS97C51H@PLCC44 [DX2044]
GMS97C51H@TQFP44 [DX3002]
GMS97C52 [DX0001]
GMS97C52@PLCC44 [DX2044]
GMS97C52@TQFP44 [DX3002]
GMS97C52H [DX0001]
GMS97C52H@PLCC44 [DX2044]
GMS97C52H@TQFP44 [DX3002]

GMS97C54 [DX0001]
GMS97C54@PLCC44 [DX2044]
GMS97C54@TQFP44 [DX3002]
GMS97C54H [DX0001]
GMS97C54H@PLCC44 [DX2044]
GMS97C54H@TQFP44 [DX3002]
GMS97C56 [DX0001]
GMS97C56@PLCC44 [DX2044]
GMS97C56@TQFP44 [DX3002]
GMS97C56H [DX0001]
GMS97C56H@PLCC44 [DX2044]
GMS97C56H@TQFP44 [DX3002]
GMS97C58 [DX0001]
GMS97C58@PLCC44 [DX2044]
GMS97C58@TQFP44 [DX3002]
GMS97C58H [DX0001]
GMS97C58H@PLCC44 [DX2044]
GMS97C58H@TQFP44 [DX3002]
GMS97L1051 [DX0001]
GMS97L1051@SOIC20 [DX1033]
GMS97L2051 [DX0001]
GMS97L2051@SOIC20 [DX1033]
GMS97L51 [DX0001]
GMS97L51@PLCC44 [DX2044]
GMS97L51@TQFP44 [DX3002]
GMS97L52 [DX0001]
GMS97L52@PLCC44 [DX2044]
GMS97L52@TQFP44 [DX3002]
GMS97L54 [DX0001]
GMS97L54@PLCC44 [DX2044]
GMS97L54@TQFP44 [DX3002]
GMS97L56 [DX0001]
GMS97L56@PLCC44 [DX2044]
GMS97L56@TQFP44 [DX3002]
GMS97L58 [DX0001]
GMS97L58@PLCC44 [DX2044]
GMS97L58@TQFP44 [DX3002]
GMS99C51 [DX0001]
GMS99C51@PLCC44 [DX2044]
GMS99C51@TQFP44 [DX3002]
GMS99C52 [DX0001]
GMS99C52@PLCC44 [DX2044]
GMS99C52@TQFP44 [DX3002]
GMS99C58 [DX0001]
GMS99C58@PLCC44 [DX2044]
GMS99C58@TQFP44 [DX3002]
HMS81004E(dip20) [DX0001]
HMS81004E(dip24) [DX0001]
HMS81004E(dip28) [DX0001]
HMS81004E@PLCC44 [DX2044]
HMS81004E@SOIC20 [DX1033]
HMS81004E@SOIC24 [DX1033]
HMS81004E@SOIC28 [DX1033]
HMS81008E(dip20) [DX0001]
HMS81008E(dip24) [DX0001]
HMS81008E(dip28) [DX0001]
HMS81008E@PLCC44 [DX2044]
HMS81008E@SOIC20 [DX1033]
HMS81008E@SOIC24 [DX1033]
HMS81008E@SOIC28 [DX1033]
HMS81016E(dip20) [DX0001]
HMS81016E(dip24) [DX0001]
HMS81016E(dip28) [DX0001]
HMS81016E@PLCC44 [DX2044]
HMS81016E@SOIC20 [DX1033]
HMS81016E@SOIC24 [DX1033]
HMS81016E@SOIC28 [DX1033]
HMS81020ET(dip20) [DX0001]
HMS81020ET(dip24) [DX0001]
HMS81020ET(dip28) [DX0001]
HMS81020ET@SOIC20 [DX1033]
HMS81020ET@SOIC24 [DX1033]
HMS81020ET@SOIC28 [DX1033]
HMS81020TL(dip20) [DX0001]
HMS81020TL(dip24) [DX0001]
HMS81020TL(dip28) [DX0001]
HMS81020TL@SOIC20 [DX1033]
HMS81020TL@SOIC24 [DX1033]
HMS81020TL@SOIC28 [DX1033]
HMS81024E(dip20) [DX0001]
HMS81024E(dip24) [DX0001]
HMS81024E(dip28) [DX0001]
HMS81024E@PLCC44 [DX2044]
HMS81024E@SOIC20 [DX1033]
HMS81024E@SOIC24 [DX1033]
HMS81024E@SOIC28 [DX1033]
HMS81032(dip20) [DX0001]
HMS81032(dip24) [DX0001]
HMS81032(dip28) [DX0001]
HMS81032@SOIC20 [DX1033]
HMS81032@SOIC24 [DX1033]
HMS81032@SOIC28 [DX1033]
HMS81032ET(dip20) [DX0001]
HMS81032ET(dip24) [DX0001]
HMS81032ET(dip28) [DX0001]
HMS81032ET@SOIC20 [DX1033]

HMS81032ET@SOIC24 [DX1033]
HMS81032ET@SOIC28 [DX1033]
HMS81032T(dip20) [DX0001]
HMS81032T(dip24) [DX0001]
HMS81032T(dip28) [DX0001]
HMS81032T@SOIC20 [DX1033]
HMS81032T@SOIC24 [DX1033]
HMS81032T@SOIC28 [DX1033]
HMS81032TL(dip20) [DX0001]
HMS81032TL(dip24) [DX0001]
HMS81032TL(dip28) [DX0001]
HMS81032TL@SOIC20 [DX1033]
HMS81032TL@SOIC24 [DX1033]
HMS81032TL@SOIC28 [DX1033]
HMS87C1102A [DX0001]
HMS87C1102A@SOP16 [DX1033]
HMS87C1104A [DX0001]
HMS87C1104A@SOP16 [DX1033]
HMS87C1202A [DX0001]
HMS87C1202A@SOP20 [DX1033]
HMS87C1204A [DX0001]
HMS87C1204A@SOP20 [DX1033]
HMS87C1302A@SDIP24 [DX0032]
HMS87C1302A@SOP24 [DX1033]
HMS87C1304A@SDIP24 [DX0032]
HMS87C1304A@SOP24 [DX1033]
HMS87C1404B [DX0001]
HMS87C1404B@SDIP28 [DX0032]
HMS87C1404B@SOIC28 [DX1033]
HMS87C1408B [DX0001]
HMS87C1408B@SDIP28 [DX0032]
HMS87C1408B@SOIC28 [DX1033]
HMS87C1416B [DX0001]
HMS87C1416B@SDIP28 [DX0032]
HMS87C1416B@SOIC28 [DX1033]
HMS87C1508B [DX0001]
HMS87C1516B [DX0001]
HMS87C1608B [DX0001]
HMS87C1616B [DX0001]
HMS87C1708B@SDIP42 [DX0042]
HMS87C1716B@SDIP42 [DX0042]
HMS87C1808B@TQFP44 [DX3002]
HMS87C1816B@TQFP44 [DX3002]
HMS87C5216 [DX0001]
HMS87C5216@PLCC44 [DX2044]
HMS87C5216@SOIC28 [DX1033]
HMS87C5216@TQFP44 [DX3002]
HMS99C51 [DX0001]
HMS99C51@PLCC44 [DX2044]
HMS99C51@TQFP44 [DX3002]
HMS99C52 [DX0001]
HMS99C52@PLCC44 [DX2044]
HMS99C52@TQFP44 [DX3002]
HMS99C58 [DX0001]
HMS99C58@PLCC44 [DX2044]
HMS99C58@TQFP44 [DX3002]
MC40P5001D@SOP20 [DX1033]
MC40P5004BD@SOP20(1K) [DX1033]
MC40P5004BD@SOP20(2K) [DX1033]
MC40P5004BD@SOP20(4K) [DX1033]
MC40P5004BR@TSSOP20(1K) [DX1067]
MC40P5004BR@TSSOP20(2K) [DX1067]
MC40P5004BR@TSSOP20(4K) [DX1067]
MC40P5101D@SOP20 [DX1033]
MC40P5104BM@SOP16(1K) [DX1016]
MC40P5104BM@SOP16(2K) [DX1016]
MC40P5104BM@SOP16(4K) [DX1016]
MC40P5201D@SOP24 [DX1033]
MC40P5204BD@SOP24(1K) [DX1033]
MC40P5204BD@SOP24(2K) [DX1033]
MC40P5204BD@SOP24(4K) [DX1033]
MC40P5301D@SOP24 [DX1033]
MC40P5404BD@SOP20(1K) [DX1033]
MC40P5404BD@SOP20(2K) [DX1033]
MC40P5404BD@SOP20(4K) [DX1033]
MC40P6004BD@SOP20(1K) [DX1033]
MC40P6004BD@SOP20(2K) [DX1033]
MC40P6004BD@SOP20(4K) [DX1033]
MC40P6004BR@TSSOP20(1K) [DX1067]
MC40P6004BR@TSSOP20(2K) [DX1067]
MC40P6004BR@TSSOP20(4K) [DX1067]
MC40P6104M@SOP16(1K) [DX1016]
MC40P6104M@SOP16(2K) [DX1016]
MC40P6104M@SOP16(4K) [DX1016]
MC80F0104 [DX0001]
MC80F0104@SOP16 [DX1033]
MC80F0104@TSSOP16 [DX1033]
MC80F0204 [DX0001]
MC80F0204@SOP20 [DX1033]
MC80F0208K@SDIP42 [DX0042]
MC80F0208Q@MQFP44 [DX3002]
MC80F0216K@SDIP42 [DX0042]
MC80F0216Q@MQFP44 [DX3002]
MC80F0224K@SDIP42 [DX0042]
MC80F0224Q@MQFP44 [DX3002]
MC80F0304 [DX0001]

MC80F0304@SOP28 [DX1033]
MC80F0308@SOP28 [DX1033]
MC80F0316@SOP28 [DX1033]
MC80F0424L@LQFP64 [DX3011]
MC80F0432K@SDIP64 [DX0064]
MC80F0432Q@MQFP64 [DX3015]
MC80F0448L@LQFP64 [DX3011]
MC80F0504 [DX0001]
MC80F0504@SSOP16 [DX1026]
MC80F0604 [DX0001]
MC80F0604@SSOP20 [DX1026]
MC80F0704@QFN28 [DX0001]
MC80F0708 [DX0001]
MC80F0708@SOP28 [DX1036]
MC80F0804@SOP32 [DX1069]
MC80F0808@SOP32 [DX1069]
MC80F1504D@SOP16 [DX1033]
MC80F1604B [DX0001]
MC80F1604R@SSOP20 [DX1067]
MC80F7108@MQFP44 [DX3002]
MC80F7308@LQFP64 [DX3011]
MC80F7408@LQFP44 [DX3003]
MC80F7708AD@SOP32 [DX1036]
MC80F7708AQ@QFP44 [DX3002]
MC80F7708Q@QFP44 [DX3002]
MC81F4104M@SOP8 [DX1045]
MC81F4204B [DX0001]
MC81F4204M@SOP16 [DX1033]
MC81F4204V [DX0001]
MC81F4215B [DX0001]
MC81F4216B [DX0001]
MC81F4315D@SOP32 [DX1069]
MC81F4315K@SDIP32 [DX0032]
MC81F4315M@SOP28 [DX1033]
MC81F4316D@SOP32 [DX1069]
MC81F4316K@SDIP32 [DX0032]
MC81F4316S@SSOP24 [DX1000]
MC81F4416Q@MQFP44 [DX3046]
MC95FG104M@SOP8 [DX1016]
MC95FG208D@SOP20 [DX1033]
MC95FG308D@SOP32 [DX1069]
MC95FG308M@SOP28 [DX1033]
MC95FG6128AL14@LQFP64 [DX3013-75]
MC95FG8128AL@LQFP80 [DX3016-75]
MC96F6332D@SOP32 [DX1069-71]
MC96F6332M@SOP28 [DX1033-71]
MC96F6332SM@SOP28 [DX1033]
MC96F6408AL@QFP48 [DX3007-72]
MC80F0308 [DX0001]
MC80F0316 [DX0001]
MC80F0424K@SDIP64 [DX0064]
MC80F0424Q@MQFP64 [DX3015]
MC80F0432L@LQFP64 [DX3011]
MC80F0448K@SDIP64 [DX0064]
MC80F0448Q@MQFP64 [DX3015]
MC80F0504@SOP16 [DX1036]
MC80F0504[153mil]@SOP16 [DX1030]
MC80F0604@SOP20 [DX1036]
MC80F0704 [DX0001]
MC80F0704@SOP28 [DX1036]
MC80F0708@QFN28 [DX0001]
MC80F0804@SDIP32 [DX0032]
MC80F0808@SDIP32 [DX0032]
MC80F1504B [DX0001]
MC80F1504R@SSOP16 [DX1067]
MC80F1604D@SOP20 [DX1033]
MC80F7108@LQFP44 [DX3003]
MC80F7208@SDIP42 [DX0042]
MC80F7308@MQFP64 [DX3015]
MC80F7408@MQFP44 [DX3002]
MC80F7708AK@SDIP32 [DX0032]
MC80F7708K@SDIP42 [DX0042]
MC81F4104B [DX0001]
MC81F4104S@SSOP10 [DX1076]
MC81F4204D@SOP20 [DX1033]
MC81F4204R@TSSOP16 [DX1000]
MC81F4204W@TSSOP20 [DX1000]
MC81F4215D@SOP20 [DX1033]
MC81F4216D@SOP20 [DX1033]
MC81F4315G [DX0001]
MC81F4315L@LQFP32 [DX3001]
MC81F4315S@SSOP24 [DX1000]
MC81F4316G [DX0001]
MC81F4316M@SOP28 [DX1033]
MC81F4416K@SDIP42 [DX0042]
MC95FG0128AL@LQFP100 [DX3021-75]
MC95FG104S@SOP10 [DX1076]
MC95FG208M@SOP16 [DX1033]
MC95FG308L@QFP32 [DX3001]
MC95FG6128AL@LQFP64 [DX3011-75]
MC95FG8128AM@MQFP80 [DX3019-75]
MC96F6332L@QFP32 [DX3001-71]
MC96F6332SD@SOP32 [DX1069]
MC96F6332SR@TSSOP28 [DX1001]
MC96F6432Q@QFP44 [DX3002-71]

MC96F6432SQ@QFP44 [DX3002]
MC96F6509LB@QFP48 [DX3007-72]
MC96F6632L@QFP64 [DX3011-72]
MC96F6832L@QFP80 [DX3016-72]
MC96F6832Q@QFP80 [DX3019-72]
MC96F7416AL@QFP48 [DX3007-71]
MC96F7416SLB@QFP48 [DX3007-71]
MC96F7616AL@QFP64 [DX3011-71]
MC96F7664L@QFP64 [DX3011-73]
MC96F7664L14@QFP64 [DX3013-73]
MC96F7816L@QFP80 [DX3016-2]
MC96F7816Q@QFP80 [DX3019-1]
MC96F7864L@LQFP80 [DX3016-73]
MC96F7864Q@MQFP80 [DX3019-73]
MC96F8208OB [DX0001-71]
MC96F8208OCD@SOP20 [DX1033-72]
MC96F8208OMN@SSOP16 [DX1016-72]
MC96F8208OU@QFN20 [DX4011-72]
MC96F8208S@DIP20 [DX0001]
MC96F8208S@QFN20 [DX4011]
MC96F8208S@SOP16 [DX1016]
MC96F8208S@SOP20 [DX1033]
MC96F8208S@TSSOP20 [DX1000]
MC96F8216B [DX0001-71]
MC96F8216D@SOP20 [DX1033-72]
MC96F8216SD@SOP20 [DX1033]
MC96F8216SU@QFN24 [DX4012]
MC96F8216U@QFN24 [DX4012-71]
MC96F8316D@SOP32 [DX1069-72]
MC96F8316G [DX0001-72]
MC96F8316L@QFP32 [DX3001-72]
MC96F8316M@SOP28 [DX1033-73]
MC96F8316R@TSSOP28 [DX1001-71]
MC96F8316SD@SOP32 [DX1033]
MC96F8316SM@SOP28 [DX1033]
MC96F8316SR@TSSOP28 [DX1001]
MC96F8316SU@QFN32 [DX4015]
MC96F8316U@QFN32 [DX4015-71]

ACE

E(E)PROM/FRAM/NVRAM

ACE24C32@SON8 [DX4047]
ACE24C64@SON8 [DX4047]

ACE Technology

E(E)PROM/FRAM/NVRAM

ACE24C02A [DX0001]
ACE24C02A@SOIC8 [DX1045]
ACE24C02A@TSSOP8 [DX1059]
ACE24C04A [DX0001]
ACE24C04A@SOIC8 [DX1045]
ACE24C04A@TSSOP8 [DX1059]
ACE24C08A [DX0001]
ACE24C08A@SOIC8 [DX1045]
ACE24C08A@TSSOP8 [DX1059]
ACE24C128 [DX0001]
ACE24C128@SOIC8 [DX1045]
ACE24C128@TSSOP8 [DX1059]
ACE24C16A [DX0001]
ACE24C16A@SOIC8 [DX1045]
ACE24C16A@TSSOP8 [DX1059]
ACE24C256 [DX0001]
ACE24C256@SOIC8 [DX1045]
ACE24C256@TSSOP8 [DX1059]
ACE24C32 [DX0001]
ACE24C32@SOIC8 [DX1045]
ACE24C32@TSSOP8 [DX1059]
ACE24C64 [DX0001]
ACE24C64@SOIC8 [DX1045]
ACE24C64@TSSOP8 [DX1059]
ACE24LC02 [DX0001]
ACE24LC02@SOIC8 [DX1045]
ACE24LC02@TSSOP8 [DX1059]
ACE24LC04 [DX0001]
ACE24LC04@SOIC8 [DX1045]
ACE24LC04@TSSOP8 [DX1059]
ACE24LC08 [DX0001]
ACE24LC08@SOIC8 [DX1045]

ACE24LC08@TSSOP8 [DX1059]
ACE24LC16 [DX0001]
ACE24LC16@SOIC8 [DX1045]
ACE24LC16@TSSOP8 [DX1059]
ACE93C46(08bit) [DX0001]
ACE93C46(08bit)@SOIC8 [DX1045]
ACE93C46(08bit)@TSSOP8 [DX1059]
ACE93C46(16bit) [DX0001]
ACE93C46(16bit)@SOIC8 [DX1045]
ACE93C46(16bit)@TSSOP8 [DX1059]

ACT

E(E)PROM/FRAM/NVRAM

93LC46(08bit) [DX0001]
93LC46(08bit)@SOIC8 [DX1045]
93LC46(16bit) [DX0001]
93LC46(16bit)@SOIC8 [DX1045]
93LC56(08bit) [DX0001]
93LC56(08bit)@SOIC8 [DX1045]
93LC56(16bit) [DX0001]
93LC56(16bit)@SOIC8 [DX1045]
93LC66(08bit) [DX0001]
93LC66(08bit)@SOIC8 [DX1045]
93LC66(16bit) [DX0001]
93LC66(16bit)@SOIC8 [DX1045]
93LC86(08bit) [DX0001]
93LC86(08bit)@SOIC8 [DX1045]
93LC86(16bit) [DX0001]
93LC86(16bit)@SOIC8 [DX1045]
ACT-F128K32N@PGA66 [DX5000]
ACT-F512K32N@PGA66 [DX5000]

ACTIVE-SEMI

MICROCONTROLLER

CST32501QF@QFN57 [DX4082]
PAC5210@QFN56 [DX4022]
PAC5220@QFN48 [DX4022]
PAC5223@QFN48 [DX4043]
PAC5250@QFN57 [DX4082]
PAC5253@QFN56 [DX4022]

ACTRANS

E(E)PROM/FRAM/NVRAM

AC25010@SOIC8 [DX1045#1]
AC25512@SOIC8 [DX1045#1]
AC25LC010@SOIC8 [DX1045#1]
AC25LC512@SOIC8 [DX1045#1]
AC39LV010@FBGA48 [DX5002]
AC39LV010@PLCC32 [DX2032]
AC39LV010@VSOP32 [DX1003]
AC39LV020@FBGA48 [DX5002]
AC39LV020@PLCC32 [DX2032]
AC39LV020@VSOP32 [DX1003]
AC39LV040@PLCC32 [DX2032]
AC39LV040@VSOP32 [DX1003]
AC39LV080@FBGA48 [DX5002]
AC39LV080@TSOP40 [DX1006]
AC39LV088@TSOP48 [DX1004]
AC39LV512@PLCC32 [DX2032]
AC39LV512@VSOP32 [DX1003]
AC39LV800@FBGA48 [DX5002]
AC39LV800@TSOP48 [DX1004]
AC39VF800@FBGA48 [DX5002]
AC39VF800@TSOP48 [DX1004]

ADESTO

E(E)PROM/FRAM/NVRAM

AT25DN512C@DFN8 [DX4002#1]
AT25DN512C@SOIC8 [DX1045#1]
AT25DN512C@TSSOP [DX1044#1]
AT25SF041@SOIC8 [DX1045#1]
AT25SF041@TSSOP8 [DX1044#1]
AT25SF041@USON8 [DX4002#1]
AT25SF081@SOIC8 [DX1045#1]
AT25SF081@TSSOP8 [DX1044#1]
AT25SF081@USON8 [DX4002#1]
AT25SF161@SOIC8 [DX1045#1]
AT25SF161@TSSOP8 [DX1044#1]
AT25SF161@USON8 [DX4002#1]
AT25XE021A@SOIC8 [DX1045#2]
AT25XE021A@TSSOP8 [DX1001#3]
AT25XE021A@UDFN8(2*3) [DX4002#1]
AT25XE021A@UDFN8(5*6) [DX4005#3]
AT45DB041E(page256)@MLF8 [DX4005#2]
AT45DB041E(page256)@SOIC8[150] [DX1016#1]
AT45DB041E(page256)@SOIC8[200] [DX1031#1]
AT45DB041E(page264)@MLF8 [DX4005-2]
AT45DB041E(page264)@SOIC8[150] [DX1016-1]
AT45DB041E(page264)@SOIC8[200] [DX1031-1]
AT45DB321E(page512)@QFN8 [DX4006]
AT45DB321E(page512)@SOIC8 [DX1050]
AT45DB321E(page512)@TSOP28 [DX1024]
AT45DB321E(page512)@UDFN8 [DX4005]
AT45DB321E(page528)@QFN8 [DX4006]
AT45DB321E(page528)@SOIC8 [DX1050]
AT45DB321E(page528)@TSOP28 [DX1024]
AT45DB321E(page528)@UDFN8 [DX4005]
AT45DB641E(page256)@SOIC8 [DX1032]
AT45DB641E(page264)@SOIC8 [DX1032]
RM24EP128A@SOIC8 [DX1045]
RM24EP128B@SOIC8 [DX1045]
RM24EP32A@SOIC8 [DX1045]
RM24EP32B@SOIC8 [DX1045]
RM24EP32C@SOIC8 [DX1045]
RM24EP64A@SOIC8 [DX1045]
RM24EP64B@SOIC8 [DX1045]
RM24EP64C@SOIC8 [DX1045]
RM25C128A@SOIC8 [DX1045]
RM25C128A@TSSOP8 [DX1059]
RM25C256A@SOIC8 [DX1045]
RM25C256A@TSSOP8 [DX1059]
RM25C32A [DX0001]
RM25C32A@SOIC8 [DX1045]
RM25C32A@TSSOP8 [DX1059]
RM25C64A [DX0001]
RM25C64A@SOIC8 [DX1045]
RM25C64A@TSSOP8 [DX1059]

ADI

MICROCONTROLLER

AD5251@TSSOP14 [DX1001]
AD5252@TSSOP14 [DX1001]
AD5253@TSSOP20 [DX1001]
AD5254@TSSOP20 [DX1001]
ADE5166@LQFP64 [DX3011]
ADE5169@LQFP64 [DX3011]
ADE5566@LQFP64 [DX3011]
ADE5569@LQFP64 [DX3011]
ADE7166F16@LFCSP64 [DX4023]
ADE7166F16@LQFP64 [DX3011]

ADE7169F16@LFCSP64 [DX4023]
ADE7169F16@LQFP64 [DX3011]
ADE7566F16@LFCSP64 [DX4023]
ADE7566F16@LQFP64 [DX3011]
ADE7569F16@LFCSP64 [DX4023]
ADE7569F16@LQFP64 [DX3011]
ADM1026@LQFP48 [DX3007]
ADM1041@QSOP24 [DX1000]
ADM1062@LFCSP40 [DX4017]
ADM1062@LQFP48 [DX3007]
ADM1063@LFCSP40 [DX4017]
ADM1063@LQFP48 [DX3007]
ADM1065@LFCSP40 [DX4017]
ADM1065@LQFP48 [DX3007]
ADM1066@LFCSP40 [DX4017]
ADM1066@LQFP48 [DX3007]
ADM1066@TSSOP28 [DX1001]
ADM1068@LQFP32 [DX3001]
ADM1069@LFCSP40 [DX4017]
ADM1069@LQFP32 [DX3001]
ADUC7020@QFN40 [DX4017]
ADUC7020BCPZ62@QFN40(UART) [DX4017]
ADUC7021BCPZ32@QFN40(UART) [DX4017]
ADUC7021BCPZ62@QFN40(UART) [DX4017]
ADUC7022BCPZ32@QFN40(UART) [DX4017]
ADUC7022BCPZ62@QFN40(UART) [DX4017]
ADUC7023@QFN40 [DX4017]
ADUC7024BCPZ62@QFN64(UART) [DX4023]
ADUC7024BSTZ62@LQFP64(UART) [DX3011]
ADUC7025BCPZ32@QFN64(UART) [DX4023]
ADUC7025BCPZ62@QFN64(UART) [DX4023]
ADUC7025BSTZ62@LQFP64(UART) [DX3011]
ADUC7026BSTZ62@LQFP80(UART) [DX3016]
ADUC7027BSTZ62@LQFP80(UART) [DX3016]
ADUC7028BBCZ62@BGA64(UART) [DX5091]
ADUC7032@LQFP48 [DX3007]
ADUC7033@LQFP48 [DX3007]
ADUC7033@QFN48 [DX4021]
ADUC7034@QFN48 [DX4021]
ADUC7036@QFN48 [DX4021]
ADUC7060@LQFP48 [DX3007]
ADUC7060@QFN48 [DX4021]
ADUC7061@QFN32 [DX4015]
ADUC7122@BGA108 [DX5150]
ADUC7128@LQFP64 [DX3011]
ADUC7128@QFN64 [DX4023]
ADUC7129@LQFP80 [DX3016]
ADUC812BCP@LFCSP56 [DX4022]
ADUC812BS@MQFP52 [DX3009]
ADuC814@SSOP28 [DX1001]
ADUC816@LFCSP56 [DX4022]
ADUC816@MQFP52 [DX3009]
ADUC824@LFCSP56 [DX4022]
ADUC824@MQFP52 [DX3009]
ADuC831BCP@LFCSP56 [DX4022]
ADuC831BS@MQFP52 [DX3009]
ADuC832BCP@LFCSP56 [DX4022]
ADuC832BS@MQFP52 [DX3009]
ADuC834BCP@LFCSP56 [DX4022]
ADuC834BS@MQFP52 [DX3009]
ADuC836BCP@LFCSP56 [DX4022]
ADuC836BS@MQFP52 [DX3009]
ADuC841BCP62@LFCSP56 [DX4022]
ADuC841BCP8@LFCSP56 [DX4022]
ADuC841BS62@MQFP52 [DX3009]
ADuC842BCP32@LFCSP56 [DX4022]
ADuC842BCP62@LFCSP56 [DX4022]
ADuC842BCP8@LFCSP56 [DX4022]
ADuC842BS62@MQFP52 [DX3009]
ADuC843BCP32@LFCSP56 [DX4022]
ADuC843BCP62@LFCSP56 [DX4022]
ADuC843BCP8@LFCSP56 [DX4022]
ADuC843BS62@MQFP52 [DX3009]
ADuC845BCP62@LFCSP56 [DX4022]
ADuC845BCP8@LFCSP56 [DX4022]
ADuC845BS62@MQFP52 [DX3009]
ADuC845BS8@MQFP52 [DX3009]
ADuC847BCP62@LFCSP56 [DX4022]
ADuC847BCP8@LFCSP56 [DX4022]
ADuC847BS32@MQFP52 [DX3009]
ADuC847BS62@MQFP52 [DX3009]

ADuC847BS8@MQFP52 [DX3009]
ADuC848BCP62@LFCSP56 [DX4022]
ADuC848BCP8@LFCSP56 [DX4022]
ADuC848BS32@MQFP52 [DX3009]
ADuC848BS62@MQFP52 [DX3009]
ADuC848BS8@MQFP52 [DX3009]
ADuCM360@LFCSP48 [DX4021]
ADuCM361@LFCSP48 [DX4021]

ADVANCE GROUP

E(E)PROM/FRAM/NVRAM

AF24BC01 [DX0001]
AF24BC01@SOIC8 [DX1045]
AF24BC01@TSOP8 [DX1059]
AF24BC02 [DX0001]
AF24BC02@SOIC8 [DX1045]
AF24BC02@TSOP8 [DX1059]
AF24BC04 [DX0001]
AF24BC04@SOIC8 [DX1045]
AF24BC04@TSOP8 [DX1059]
AF24BC08 [DX0001]
AF24BC08@SOIC8 [DX1045]
AF24BC08@TSOP8 [DX1059]
AF24BC16 [DX0001]
AF24BC16@SOIC8 [DX1045]
AF24BC16@TSOP8 [DX1059]
AF24C128 [DX0001]
AF24C128@SOIC8 [DX1045]
AF24C128@TSOP8 [DX1059]
AF24C256 [DX0001]
AF24C256@SOIC8 [DX1045]
AF24C256@TSOP8 [DX1059]
AF24C32 [DX0001]
AF24C32@SOIC8 [DX1045]
AF24C32@TSOP8 [DX1059]
AF24C64 [DX0001]
AF24C64@SOIC8 [DX1045]
AF24C64@TSOP8 [DX1059]
AF93C46(08bit) [DX0001]
AF93C46(08bit)@SOIC8 [DX1045]
AF93C46(08bit)@TSOP8 [DX1059]
AF93C46(16bit) [DX0001]
AF93C46(16bit)@SOIC8 [DX1045]
AF93C46(16bit)@TSOP8 [DX1059]
AF93C56(08bit) [DX0001]
AF93C56(08bit)@SOIC8 [DX1045]
AF93C56(08bit)@TSOP8 [DX1059]
AF93C56(16bit) [DX0001]
AF93C56(16bit)@SOIC8 [DX1045]
AF93C56(16bit)@TSOP8 [DX1059]
AF93C66(08bit) [DX0001]
AF93C66(08bit)@SOIC8 [DX1045]
AF93C66(08bit)@TSOP8 [DX1059]
AF93C66(16bit) [DX0001]
AF93C66(16bit)@SOIC8 [DX1045]
AF93C66(16bit)@TSOP8 [DX1059]
AF93C86(08bit) [DX0001]
AF93C86(08bit)@SOIC8 [DX1045]
AF93C86(08bit)@TSOP8 [DX1059]
AF93C86(16bit) [DX0001]
AF93C86(16bit)@SOIC8 [DX1045]
AF93C86(16bit)@TSOP8 [DX1059]

MICROCONTROLLER

AG89P51
AG89P51@PLCC44
AG89P51@PQFP44
AG89P51A
AG89P51A@PLCC44
AG89P51A@PQFP44
AG89P52
AG89P52@PLCC44
AG89P52@PQFP44

AEROFLEX

E(E)PROM/FRAM/NVRAM

ACT-F512K32N@PGA66 [DX5000]
ACT-F512K8N [DX0001]
ACT-SF128K16N@PGA66 [DX5000]

AIROHA

MICROCONTROLLER

AB1128@QFN40 [DX4039]

AiT Semiconductor

E(E)PROM/FRAM/NVRAM

A24C02 [DX0001]
A24C02@SOP8 [DX1045]
A24C02@SOT23-5 [DX1041]
A24C02@TSSOP8 [DX1059]
A24C04 [DX0001]
A24C04@SOP8 [DX1045]
A24C04@SOT23-5 [DX1041]
A24C04@TSSOP8 [DX1059]
A24C08 [DX0001]
A24C08@SOP8 [DX1045]
A24C08@SOT23-5 [DX1041]
A24C08@TSSOP8 [DX1059]
A24C128@SOP8 [DX1045]
A24C128@TSSOP8 [DX1059]
A24C16 [DX0001]
A24C16@SOP8 [DX1045]
A24C16@SOT23-5 [DX1041]
A24C16@TSSOP8 [DX1059]
A24C256@SOP8 [DX1045]
A24C256@TSSOP8 [DX1059]
A24C32@DFN8 [DX4047]
A24C32@SOP8 [DX1045]
A24C32@TSSOP8 [DX1059]
A24C64@SOP8 [DX1045]
A24C64@TSSOP8 [DX1059]
A93C46(08bit)@SOP8 [DX1045]
A93C46(08bit)@tsSOP8 [DX1059]
A93C46(16bit)@SOP8 [DX1045]
A93C46(16bit)@TSSOP8 [DX1059]
A93C56(08bit)@SOP8 [DX1045]
A93C56(08bit)@tsSOP8 [DX1059]
A93C56(16bit)@SOP8 [DX1045]
A93C56(16bit)@TSSOP8 [DX1059]
A93C66(08bit)@SOP8 [DX1045]
A93C66(08bit)@tsSOP8 [DX1059]
A93C66(16bit)@SOP8 [DX1045]
A93C66(16bit)@TSSOP8 [DX1059]

ALI(Acer)

E(E)PROM/FRAM/NVRAM

M8720 [DX0001]
M8720@PLCC32 [DX2032]

MICROCONTROLLER

M6759 [DX0001]
M6759@PLCC44 [DX2044]

M6759@TQFP44 [DX3002]

ALL24SERIES

E(E)PROM/FRAM/NVRAM

24C01(ISP) [DX0001]
24C02(ISP) [DX0001]
24C04(ISP) [DX0001]
24C08(ISP) [DX0001]
24C128(ISP) [DX0001]
24C16(ISP) [DX0001]
24C256(ISP) [DX0001]
24C32(ISP) [DX0001]
24C64(ISP) [DX0001]

ALLFLASH

E(E)PROM/FRAM/NVRAM

AFA1G08T@TSOP48 [DX1004-3]

ALLIANCE

E(E)PROM/FRAM/NVRAM

AS29F200B@PSOP44 [DX1014]
AS29F200B@TSOP48 [DX1004]
AS29F200T@PSOP44 [DX1014]
AS29F200T@TSOP48 [DX1004]
AS29LV160B@TSOP48 [DX1004]
AS29LV160T@TSOP48 [DX1004]
AS29LV400B@TSOP48 [DX1004]
AS29LV400T@TSOP48 [DX1004]
AS29LV800B@TSOP48 [DX1004]
AS29LV800T@TSOP48 [DX1004]

ALTCO

MICROCONTROLLER

ST72F321AR6T3 [DX3011]
ST72F321AR6T6 [DX3011]
ST72F321AR6TA [DX3011]
ST72F321AR7T3 [DX3011]
ST72F321AR7T6 [DX3011]
ST72F321AR7TA [DX3011]
ST72F321AR9T3 [DX3011]
ST72F321AR9T6 [DX3011]
ST72F321AR9TA [DX3011]
ST72F321AR9TC [DX3011]
ST72F321BAR6T3 [DX3011]
ST72F321BAR6T6 [DX3011]
ST72F321BAR6TA [DX3011]
ST72F321BAR7T3 [DX3011]
ST72F321BAR7T6 [DX3011]
ST72F321BAR7TA [DX3011]
ST72F321BAR9T3 [DX3011]
ST72F321BAR9T6 [DX3011]
ST72F321BAR9TA [DX3011]
ST72F321BAR9TC [DX3011]
ST72F321BJ6T3 [DX3003]
ST72F321BJ6T6 [DX3003]
ST72F321BJ6TA [DX3003]
ST72F321BJ7T3 [DX3003]
ST72F321BJ7T6 [DX3003]
ST72F321BJ7TA [DX3003]

ST72F321BJ9T3 [DX3003]
ST72F321BJ9T6 [DX3003]
ST72F321BJ9TA [DX3003]
ST72F321BJ9TC [DX3003]
ST72F321BM9T3 [DX3054]
ST72F321BM9T6 [DX3054]
ST72F321BM9TC [DX3054]
ST72F321BR6T3 [DX3013]
ST72F321BR6T6 [DX3013]
ST72F321BR6TA [DX3013]
ST72F321BR7T3 [DX3013]
ST72F321BR7T6 [DX3013]
ST72F321BR7TA [DX3013]
ST72F321BR9T3 [DX3013]
ST72F321BR9T6 [DX3013]
ST72F321BR9TA [DX3013]
ST72F321BR9TC [DX3013]
ST72F321J6T3 [DX3003]
ST72F321J6T6 [DX3003]
ST72F321J6TA [DX3003]
ST72F321J7T3 [DX3003]
ST72F321J7T6 [DX3003]
ST72F321J7TA [DX3003]
ST72F321J9T3 [DX3003]
ST72F321J9T6 [DX3003]
ST72F321J9TA [DX3003]
ST72F321J9TC [DX3003]
ST72F321M9T3 [DX3054]
ST72F321M9T6 [DX3054]
ST72F321M9TC [DX3054]
ST72F321R6T3 [DX3013]
ST72F321R6T6 [DX3013]
ST72F321R6TA [DX3013]
ST72F321R7T3 [DX3013]
ST72F321R7T6 [DX3013]
ST72F321R7TA [DX3013]
ST72F321R9T3 [DX3013]
ST72F321R9T6 [DX3013]
ST72F321R9TA [DX3013]
ST72F321R9TC [DX3013]
ST72F324BJ2B3 [DX0042]
ST72F324BJ2B5 [DX0042]
ST72F324BJ2B6 [DX0042]
ST72F324BJ2BA [DX0042]
ST72F324BJ2BC [DX0042]
ST72F324BJ2T3 [DX3003]
ST72F324BJ2T5 [DX3003]
ST72F324BJ2T6 [DX3003]
ST72F324BJ2TA [DX3003]
ST72F324BJ2TC [DX3003]
ST72F324BJ4B3 [DX0042]
ST72F324BJ4B5 [DX0042]
ST72F324BJ4B6 [DX0042]
ST72F324BJ4BA [DX0042]
ST72F324BJ4BC [DX0042]
ST72F324BJ4T3 [DX3003]
ST72F324BJ4T5 [DX3003]
ST72F324BJ4T6 [DX3003]
ST72F324BJ4TA [DX3003]
ST72F324BJ4TC [DX3003]
ST72F324BJ6B3 [DX0042]
ST72F324BJ6B5 [DX0042]
ST72F324BJ6B6 [DX0042]
ST72F324BJ6BA [DX0042]
ST72F324BJ6BC [DX0042]
ST72F324BJ6T3 [DX3003]
ST72F324BJ6T5 [DX3003]
ST72F324BJ6T6 [DX3003]
ST72F324BJ6TA [DX3003]
ST72F324BJ6TC [DX3003]
ST72F324BK2B3 [DX0032]
ST72F324BK2B5 [DX0032]
ST72F324BK2B6 [DX0032]
ST72F324BK2BA [DX0032]
ST72F324BK2BC [DX0032]
ST72F324BK2T3 [DX3001]
ST72F324BK2T5 [DX3001]
ST72F324BK2T6 [DX3001]
ST72F324BK2TA [DX3001]
ST72F324BK2TC [DX3001]
ST72F324BK4B3 [DX0032]
ST72F324BK4B5 [DX0032]
ST72F324BK4B6 [DX0032]
ST72F324BK4BA [DX0032]
ST72F324BK4BC [DX0032]
ST72F324BK4T3 [DX3001]
ST72F324BK4T5 [DX3001]
ST72F324BK4T6 [DX3001]
ST72F324BK4TA [DX3001]
ST72F324BK4TC [DX3001]
ST72F324BK6B3 [DX0032]
ST72F324BK6B5 [DX0032]
ST72F324BK6B6 [DX0032]
ST72F324BK6BA [DX0032]
ST72F324BK6BC [DX0032]
ST72F324BK6T3 [DX3001]

ST72F324BK6T5 [DX3001]
ST72F324BK6T6 [DX3001]
ST72F324BK6TA [DX3001]
ST72F324BK6TC [DX3001]
ST72F324J2B3 [DX0042]
ST72F324J2B5 [DX0042]
ST72F324J2B6 [DX0042]
ST72F324J2BA [DX0042]
ST72F324J2BC [DX0042]
ST72F324J2T3 [DX3003]
ST72F324J2T5 [DX3003]
ST72F324J2T6 [DX3003]
ST72F324J2TA [DX3003]
ST72F324J2TC [DX3003]
ST72F324J4B3 [DX0042]
ST72F324J4B5 [DX0042]
ST72F324J4B6 [DX0042]
ST72F324J4BA [DX0042]
ST72F324J4BC [DX0042]
ST72F324J4T3 [DX3003]
ST72F324J4T5 [DX3003]
ST72F324J4T6 [DX3003]
ST72F324J4TA [DX3003]
ST72F324J4TC [DX3003]
ST72F324J6B3 [DX0042]
ST72F324J6B5 [DX0042]
ST72F324J6B6 [DX0042]
ST72F324J6BA [DX0042]
ST72F324J6BC [DX0042]
ST72F324J6T3 [DX3003]
ST72F324J6T5 [DX3003]
ST72F324J6T6 [DX3003]
ST72F324J6TA [DX3003]
ST72F324J6TC [DX3003]
ST72F324K2B3 [DX0032]
ST72F324K2B5 [DX0032]
ST72F324K2B6 [DX0032]
ST72F324K2BA [DX0032]
ST72F324K2BC [DX0032]
ST72F324K2T3 [DX3001]
ST72F324K2T5 [DX3001]
ST72F324K2T6 [DX3001]
ST72F324K2TA [DX3001]
ST72F324K2TC [DX3001]
ST72F324K4B3 [DX0032]
ST72F324K4B5 [DX0032]
ST72F324K4B6 [DX0032]
ST72F324K4BA [DX0032]
ST72F324K4BC [DX0032]
ST72F324K4T3 [DX3001]
ST72F324K4T5 [DX3001]
ST72F324K4T6 [DX3001]
ST72F324K4TA [DX3001]
ST72F324K4TC [DX3001]
ST72F324K6B3 [DX0032]
ST72F324K6B5 [DX0032]
ST72F324K6B6 [DX0032]
ST72F324K6BA [DX0032]
ST72F324K6BC [DX0032]
ST72F324K6T3 [DX3001]
ST72F324K6T5 [DX3001]
ST72F324K6T6 [DX3001]
ST72F324K6TA [DX3001]
ST72F324K6TC [DX3001]
ST72F324LJ2B3 [DX0042]
ST72F324LJ2B5 [DX0042]
ST72F324LJ2B6 [DX0042]
ST72F324LJ2BA [DX0042]
ST72F324LJ2BC [DX0042]
ST72F324LJ2T3 [DX3003]
ST72F324LJ2T5 [DX3003]
ST72F324LJ2T6 [DX3003]
ST72F324LJ2TA [DX3003]
ST72F324LJ2TC [DX3003]
ST72F324LJ4B3 [DX0042]
ST72F324LJ4B5 [DX0042]
ST72F324LJ4B6 [DX0042]
ST72F324LJ4BA [DX0042]
ST72F324LJ4BC [DX0042]
ST72F324LJ4T3 [DX3003]
ST72F324LJ4T5 [DX3003]
ST72F324LJ4T6 [DX3003]
ST72F324LJ4TA [DX3003]
ST72F324LJ4TC [DX3003]
ST72F324LJ6B3 [DX0042]
ST72F324LJ6B5 [DX0042]
ST72F324LJ6B6 [DX0042]
ST72F324LJ6BA [DX0042]
ST72F324LJ6BC [DX0042]
ST72F324LJ6T3 [DX3003]
ST72F324LJ6T5 [DX3003]
ST72F324LJ6T6 [DX3003]
ST72F324LJ6TA [DX3003]
ST72F324LJ6TC [DX3003]
ST72F324LK2B3 [DX0032]
ST72F324LK2B5 [DX0032]

ST72F324LK2B6 [DX0032]
ST72F324LK2BA [DX0032]
ST72F324LK2BC [DX0032]
ST72F324LK2T3 [DX3001]
ST72F324LK2T5 [DX3001]
ST72F324LK2T6 [DX3001]
ST72F324LK2TA [DX3001]
ST72F324LK2TC [DX3001]
ST72F324LK4B3 [DX0032]
ST72F324LK4B5 [DX0032]
ST72F324LK4B6 [DX0032]
ST72F324LK4BA [DX0032]
ST72F324LK4BC [DX0032]
ST72F324LK4T3 [DX3001]
ST72F324LK4T5 [DX3001]
ST72F324LK4T6 [DX3001]
ST72F324LK4TA [DX3001]
ST72F324LK4TC [DX3001]
ST72F324LK6B3 [DX0032]
ST72F324LK6B5 [DX0032]
ST72F324LK6B6 [DX0032]
ST72F324LK6BA [DX0032]
ST72F324LK6BC [DX0032]
ST72F324LK6T3 [DX3001]
ST72F324LK6T5 [DX3001]
ST72F324LK6T6 [DX3001]
ST72F324LK6TA [DX3001]
ST72F324LK6TC [DX3001]
ST72F325AR6T3 [DX3011]
ST72F325AR6T5 [DX3011]
ST72F325AR6T6 [DX3011]
ST72F325AR7T3 [DX3011]
ST72F325AR7T5 [DX3011]
ST72F325AR7T6 [DX3011]
ST72F325AR9T3 [DX3011]
ST72F325AR9T5 [DX3011]
ST72F325AR9T6 [DX3011]
ST72F325C4T3 [DX3007]
ST72F325C4T5 [DX3007]
ST72F325C4T6 [DX3007]
ST72F325C6T3 [DX3007]
ST72F325C6T5 [DX3007]
ST72F325C6T6 [DX3007]
ST72F325C7T3 [DX3007]
ST72F325C7T5 [DX3007]
ST72F325C7T6 [DX3007]
ST72F325C9T3 [DX3007]
ST72F325C9T5 [DX3007]
ST72F325C9T6 [DX3007]
ST72F325J4B3 [DX0042]
ST72F325J4B5 [DX0042]
ST72F325J4B6 [DX0042]
ST72F325J4T3 [DX3003]
ST72F325J4T5 [DX3003]
ST72F325J4T6 [DX3003]
ST72F325J6B3 [DX0042]
ST72F325J6B5 [DX0042]
ST72F325J6B6 [DX0042]
ST72F325J6T3 [DX3003]
ST72F325J6T5 [DX3003]
ST72F325J6T6 [DX3003]
ST72F325J7T3 [DX3003]
ST72F325J7T5 [DX3003]
ST72F325J7T6 [DX3003]
ST72F325J9T3 [DX3003]
ST72F325J9T5 [DX3003]
ST72F325J9T6 [DX3003]
ST72F325K4B3 [DX0032]
ST72F325K4B5 [DX0032]
ST72F325K4B6 [DX0032]
ST72F325K4T3 [DX3001]
ST72F325K4T5 [DX3001]
ST72F325K4T6 [DX3001]
ST72F325K6B3 [DX0032]
ST72F325K6B5 [DX0032]
ST72F325K6B6 [DX0032]
ST72F325K6T3 [DX3001]
ST72F325K6T5 [DX3001]
ST72F325K6T6 [DX3001]
ST72F325R6T3 [DX3013]
ST72F325R6T5 [DX3013]
ST72F325R6T6 [DX3013]
ST72F325R7T3 [DX3013]
ST72F325R7T5 [DX3013]
ST72F325R7T6 [DX3013]
ST72F325R9T3 [DX3013]
ST72F325R9T5 [DX3013]
ST72F325R9T6 [DX3013]
ST72F521AR6T3 [DX3011]
ST72F521AR6T6 [DX3011]
ST72F521AR6TC [DX3011]
ST72F521AR9T3 [DX3011]
ST72F521AR9T6 [DX3011]
ST72F521AR9TC [DX3011]
ST72F521BAR6T3 [DX3011]
ST72F521BAR6T6 [DX3011]

ST72F521BAR6TC [DX3011]
ST72F521BAR9T3 [DX3011]
ST72F521BAR9T6 [DX3011]
ST72F521BAR9TC [DX3011]
ST72F521BM9T3 [DX3054]
ST72F521BM9T6 [DX3054]
ST72F521BM9TC [DX3054]
ST72F521BR6T3 [DX3013]
ST72F521BR6T6 [DX3013]
ST72F521BR6TC [DX3013]
ST72F521BR9T3 [DX3013]
ST72F521BR9T6 [DX3013]
ST72F521BR9TC [DX3013]
ST72F521M9T3 [DX3054]
ST72F521M9T6 [DX3054]
ST72F521M9TC [DX3054]
ST72F521R6T3 [DX3013]
ST72F521R6T6 [DX3013]
ST72F521R6TC [DX3013]
ST72F521R9T3 [DX3013]
ST72F521R9T6 [DX3013]
ST72F521R9TC [DX3013]

ALTERA

E(E)PROM/FRAM/NVRAM

EPC1(LC)@PLCC20 [DX2020]
EPC1(LI)@PLCC20 [DX2020]
EPC1(PC8) [DX0001]
EPC1(PI8) [DX0001]
EPC1213-LC20 [DX2020]
EPC1213-LI20 [DX2020]
EPC1213-PC8 [DX0001]
EPC1213-PI8 [DX0001]
EPC1441(LC)@PLCC20 [DX2020]
EPC1441(LI)@PLCC20 [DX2020]
EPC1441(PC8) [DX0001]
EPC1441(PI8) [DX0001]
EPC1441(TC)@TQFP32 [DX3001]
EPC1441(TI)@TQFP32 [DX3001]
EPC16QC100@PQFP100 [DX3045]
EPC16QI100@PQFP100 [DX3045]
EPC16UC88@BGA88 [DX5001]
EPC16UC88AA@BGA88 [DX5001]
EPC16UC88AB@BGA88 [DX5001]
EPC16UC88N@BGA88 [DX5001]
EPC16UI88AA@BGA88 [DX5001]
EPC2(LC)@PLCC20 [DX2020]
EPC2(LI)@PLCC20 [DX2020]
EPC2(TC)@TQFP32 [DX3001]
EPC2(TI)@TQFP32 [DX3001]
EPC4QC100@PQFP100 [DX3045]
EPC4QC100N@PQFP100 [DX3045]
EPC4QI100@PQFP100 [DX3045]
EPC8QC100@PQFP100 [DX3045]
EPC8QC100DM@PQFP100 [DX3045]
EPC8QI100@PQFP100 [DX3045]
EPCQ128@SOIC16 [DX1033#1]
EPCQ16@SOIC8 [DX1045#1]
EPCQ256@SOIC16 [DX1033#1]
EPCQ32@SOIC8 [DX1045#1]
EPCQ64@SOIC16 [DX1033#1]
EPCS128@SOIC16 [DX1033#1]
EPCS16@SOIC16 [DX1033#1]
EPCS16@SOIC8 [DX1045#1]
EPCS16N@SOIC16 [DX1033#1]
EPCS1SI8@SOIC8 [DX1016]
EPCS4SI8@SOIC8 [DX1016]
EPCS64@SOIC16 [DX1033#1]

PLD

5M1270Z@fpBGA256 [DX5021]
5M1270Z@TQFP144 [DX3035]
5M160Z@EQFP64 [DX3085-2]
5M160Z@MBGA100 [DX5142]
5M160Z@MBGA68 [DX5191]
5M160Z@TQFP100 [DX3021]
5M240Z@MBGA100 [DX5142]
5M240Z@MBGA68 [DX5191]
5M240Z@TQFP100 [DX3021]
5M240Z@TQFP144 [DX3035]

5M40Z@EQFP64 [DX3085-2]
5M570Z@FBGA256 [DX5021]
5M570Z@MBGA100 [DX5142]
5M570Z@TQFP100 [DX3021]
5M570Z@TQFP144 [DX3035]
5M80Z@EQFP64 [DX3085-2]
5M80Z@MBGA68 [DX5191]
5M80Z@TQFP100 [DX3021]
EP1800@PLCC68 [DX2068]
EP1810@PLCC68 [DX2068]
EP1810T@PLCC68 [DX2068]
EP1830@PLCC68 [DX2068]
EP310 [DX0001]
EP310@PLCC20 [DX2020]
EP320 [DX0001]
EP320@PLCC20 [DX2020]
EP330 [DX0001]
EP330@PLCC20 [DX2020]
EP600 [DX0001]
EP600@PLCC28 [DX2028]
EP600@SOIC24 [DX1033]
EP600I [DX0001]
EP600I@PLCC28 [DX2028]
EP600I@SOIC24 [DX1033]
EP610 [DX0001]
EP610@PLCC28 [DX2028]
EP610@SOIC24 [DX1033]
EP610A [DX0001]
EP610A@PLCC28 [DX2028]
EP610A@SOIC24 [DX1033]
EP610I [DX0001]
EP610I@PLCC28 [DX2028]
EP610I@SOIC24 [DX1033]
EP610T [DX0001]
EP610T@PLCC28 [DX2028]
EP610T@SOIC24 [DX1033]
EP630 [DX0001]
EP630@PLCC28 [DX2028]
EP630@SOIC24 [DX1033]
EP900 [DX0001]
EP900@PLCC44 [DX2044]
EP900I [DX0001]
EP900I@PLC44 [DX2044]
EP910 [DX0001]
EP910@PLCC44 [DX2044]
EP910A [DX0001]
EP910A@PLCC44 [DX2044]
EP910I [DX0001]
EP910I@PLCC44 [DX2044]
EP910T [DX0001]
EP910T@PLCC44 [DX2044]
EPM1270@FBGA256 [DX5021]
EPM1270@TQFP144 [DX3035]
EPM1270ES@TQFP144 [DX3035]
EPM1270G@FBGA256 [DX5021]
EPM1270G@TQFP144 [DX3035]
EPM2210@FBGA256 [DX5021]
EPM2210G@FBGA256 [DX5021]
EPM240@FBGA100 [DX5059]
EPM240@MBGA100 [DX5142]
EPM240@TQFP100 [DX3021]
EPM240G@FBGA100 [DX5059]
EPM240G@MBGA100 [DX5142]
EPM240G@TQFP100 [DX3021]
EPM240Z@MBGA100 [DX5142]
EPM240Z@MBGA68 [DX5191]
EPM3032A@PLCC44 [DX2044]
EPM3032A@TQFP44 [DX3003]
EPM3064A@PLCC44 [DX2044]
EPM3064A@TQFP100 [DX3021]
EPM3064A@TQFP44 [DX3003]
EPM3128A@TQFP100 [DX3021]
EPM3128A@TQFP144 [DX3035]
EPM3256A@PQFP208(*) [DX3115]
EPM3256A@TQFP144 [DX3035]
EPM3512A@FBGA256(*) [DX3115]
EPM5032A [DX0001]
EPM5032A@PLCC28 [DX2028]
EPM5128A@PGA68 [DX5000]
EPM5128A@PLCC68 [DX2068]
EPM5130A@PLCC84 [DX2084]
EPM5130A@PQFP100 [DX3022]
EPM570@FBGA100 [DX5059]
EPM570@MBGA100 [DX5142]
EPM570@TQFP100 [DX3021]
EPM570@TQFP144 [DX3035]
EPM570F256@BGA256(*) [DX5021]
EPM570G@FBGA100 [DX5059]
EPM570G@MBGA100 [DX5142]
EPM570G@TQFP100 [DX3021]
EPM570G@TQFP144 [DX3035]
EPM570GF256@BGA256(*) [DX5021]
EPM7032@PLCC44 [DX2044]
EPM7032@TQFP44 [DX3003]
EPM7032AE@JLCC44(7032 mode) [DX2044]

EPM7032AE@PLCC44(7032 mode) [DX2044]
EPM7032AE@PLCC44(7032AE mode) [DX2044]
EPM7032AE@PLCC44(7032S mode) [DX2044]
EPM7032AE@PQFP44(7032 mode) [DX3003]
EPM7032AE@TQFP44(7032 mode) [DX3003]
EPM7032AE@TQFP44(7032AE mode) [DX3003]
EPM7032AE@TQFP44(7032S mode) [DX3003]
EPM7032S@PLCC44(7032 mode) [DX2044]
EPM7032S@PLCC44(7032S mode) [DX2044]
EPM7032S@TQFP44(7032 mode) [DX3003]
EPM7032S@TQFP44(7032S mode) [DX3003]
EPM7032V@PLCC44 [DX2044] EPM7032V@TQFP44 [DX3003]
EPM7064@PLCC44 [DX2044] EPM7064@PLCC68 [DX2068]
EPM7064@PLCC84 [DX2084] EPM7064@PQFP100 [DX3022]
EPM7064@TQFP44 [DX3003]
EPM7064AE@FBGA100(7064AE mode) [DX5059]
EPM7064AE@FBGA100(7064S mode) [DX5059]
EPM7064AE@PLCC44(7064AE mode) [DX2044]
EPM7064AE@PLCC44(7064S mode) [DX2044]
EPM7064AE@PLCC84(7064AE mode) [DX2084]
EPM7064AE@PLCC84(7064S mode) [DX2084]
EPM7064AE@TQFP100(7064AE mode) [DX3021]
EPM7064AE@TQFP100(7064S mode) [DX3021]
EPM7064AE@TQFP44(7064AE mode) [DX3003]
EPM7064AE@TQFP44(7064S mode) [DX3003]
EPM7064AE@UBGA49(7064AE mode) [DX5112]
EPM7064AE@UBGA49(7064S mode) [DX5112]
EPM7064S@PLCC44(7064 mode) [DX2044]
EPM7064S@PLCC44(7064S mode) [DX2044]
EPM7064S@PLCC68(7064 mode) [DX2068]
EPM7064S@PLCC68(7064S mode) [DX2068]
EPM7064S@PLCC84(7064 mode) [DX2084]
EPM7064S@PLCC84(7064S mode) [DX2084]
EPM7064S@PQFP100(7064 mode) [DX3022]
EPM7064S@PQFP100(7064S mode) [DX3022]
EPM7064S@TQFP100(7064 mode) [DX3021]
EPM7064S@TQFP100(7064S mode) [DX3021]
EPM7064S@TQFP44(7064 mode) [DX3003]
EPM7064S@TQFP44(7064S mode) [DX3003]
EPM7096@PLCC68 [DX2068] EPM7096@PLCC84 [DX2084]
EPM7096@PQFP100 [DX3022]
EPM7128AE@PLCC84(7128AE mode) [DX2084]
EPM7128AE@TQFP100(7128AE mode) [DX3021]
EPM7128ALC(I)84(7128 mode) [DX2084]
EPM7128ALC(I)84(7128E mode) [DX2084]
EPM7128ALC84(7128S/A mode) [DX2084]
EPM7128ALI84(7128S/A mode) [DX2084]
EPM7128AQC(I)100(7128 mode) [DX3022]

EPM7128AQC(I)100(7128E mode) [DX3022]
EPM7128AQC(I)160(7128 mode) [DX3073]
EPM7128AQC(I)160(7128E mode) [DX3073]
EPM7128AQC100(7128S/A mode) [DX3022]
EPM7128AQC160(7128S/A mode) [DX3073]
EPM7128AQI100(7128S/A mode) [DX3022]
EPM7128AQI160(7128S/A mode) [DX3073]
EPM7128ATC100(7128S/A mode) [DX3021]
EPM7128ATI100(7128S/A mode) [DX3021]
EPM7128B@FBGA100(7128B mode) [DX5059]
EPM7128B@FBGA49(7128B mode) [DX5112]
EPM7128B@TQFP100(7128B mode) [DX3021]
EPM7128B@TQFP144(7128B mode) [DX3035]
EPM7128B@VTQFP48(7128B mode) [DX3007]
EPM7128ELC(I)84(7128 mode) [DX2084]
EPM7128ELC84(7128E mode) [DX2084]
EPM7128ELI84(7128E mode) [DX2084]
EPM7128EQC(I)100(7128 mode) [DX3022]
EPM7128EQC(I)160(7128 mode) [DX3073]
EPM7128EQC100(7128E mode) [DX3022]
EPM7128EQC160(7128E mode) [DX3073]
EPM7128EQI100(7128E mode) [DX3022]
EPM7128EQI160(7128E mode) [DX3073]
EPM7128SLC(I)84(7128 mode) [DX2084]
EPM7128SLC(I)84(7128E mode) [DX2084]
EPM7128SLC84(7128S/A mode) [DX2084]
EPM7128SLI84(7128S/A mode) [DX2084]
EPM7128SQC(I)100(7128 mode) [DX3022]
EPM7128SQC(I)100(7128E mode) [DX3022]
EPM7128SQC(I)160(7128 mode) [DX3073]
EPM7128SQC(I)160(7128E mode) [DX3073]
EPM7128SQC100(7128S/A mode) [DX3022]
EPM7128SQC160(7128S/A mode) [DX3073]
EPM7128SQI100(7128S/A mode) [DX3022]
EPM7128SQI160(7128S/A mode) [DX3073]
EPM7128STC100(7128S/A mode) [DX3021]
EPM7128STI100(7128S/A mode) [DX3021]
EPM7160ELC(I)84(7160 mode) [DX2084]
EPM7160ELC84(7160E mode) [DX2084]
EPM7160ELI84(7160E mode) [DX2084]
EPM7160EQC(I)160(7160 mode) [DX3104]
EPM7160EQC100(7160E mode) [DX3022]
EPM7160EQC160(7160E mode) [DX3104]
EPM7160EQI100(7160E mode) [DX3022]
EPM7160EQI160(7160E mode) [DX3104]
EPM7160S@LC84(7160 mode) [DX2084]
EPM7160S@LC84(7160E mode) [DX2084]
EPM7160S@LC84(7160S mode) [DX2084]

EPM7160S@LI84(7160 mode) [DX2084]
EPM7160S@LI84(7160E mode) [DX2084]
EPM7160S@LI84(7160S mode) [DX2084]
EPM7160S@QC100(7160E mode) [DX3022]
EPM7160S@QC100(7160S mode) [DX3022]
EPM7160S@QC160(7160 mode) [DX3104]
EPM7160S@QC160(7160E mode) [DX3104]
EPM7160S@QC160(7160S mode) [DX3104]
EPM7160S@QI100(7160E mode) [DX3022]
EPM7160S@QI100(7160S mode) [DX3022]
EPM7160S@QI160(7160 mode) [DX3104]
EPM7160S@QI160(7160E mode) [DX3104]
EPM7160S@QI160(7160S mode) [DX3104]
EPM7160S@TC100(7160E mode) [DX3021]
EPM7160S@TC100(7160S mode) [DX3021]
EPM7160S@TI100(7160E mode) [DX3021]
EPM7160S@TI100(7160S mode) [DX3021]
EPM7192EQC(QI)160(7192 mode) [DX3104]
EPM7192EQC160(7192E mode) [DX3104]
EPM7192EQI160(7192E mode) [DX3104]
EPM7256A@PQFP208(7256 mode) [DX3095]
EPM7256A@PQFP208(7256A/S mode) [DX3095]
EPM7256A@PQFP208(7256E mode) [DX3095]
EPM7256A@TQFP100(7256A/S mode) [DX3021]
EPM7256A@TQFP144(7256A/S mode) [DX3035]
EPM7256AE@FBGA100(7256A mode) [DX5059]
EPM7256AE@FBGA100(7256AE mode) [DX5059]
EPM7256AE@FBGA100(7256S mode) [DX5059]
EPM7256AE@TQFP100(7256A mode) [DX3021]
EPM7256AE@TQFP100(7256AE mode) [DX3021]
EPM7256AE@TQFP100(7256S mode) [DX3021]
EPM7256AE@TQFP144(7256A mode) [DX3035]
EPM7256AE@TQFP144(7256AE mode) [DX3035]
EPM7256AE@TQFP144(7256S mode) [DX3035]
EPM7256E@GC192(7256 mode) [DX5117]
EPM7256E@GC192(7256E mode) [DX5117]
EPM7256E@GI192(7256 mode) [DX5117]
EPM7256E@GI192(7256E mode) [DX5117]
EPM7256E@QC160(7256E mode) [DX3038]
EPM7256E@QI160(7256E mode) [DX3038]
EPM7256E@RC208(7256 mode) [DX3082]
EPM7256E@RC208(7256E mode) [DX3082]
EPM7256E@RI208(7256 mode) [DX3082]
EPM7256E@RI208(7256E mode) [DX3082]
EPM7256S@PGA192(7256E mode) [DX5117]
EPM7256S@PGA192(7256S/A mode) [DX5117]
EPM7256S@PQFP208(7256 mode) [DX3082]
EPM7256S@PQFP208(7256E mode) [DX3082]

EPM7256S@PQFP208(7256S/A mode) [DX3082]
EPM7256S@RQFP208(7256 mode) [DX3082]
EPM7256S@RQFP208(7256E mode) [DX3082]
EPM7256S@RQFP208(7256S/A mode) [DX3082]
EPM7256S@TQFP160(7256E mode) [DX3038]
EPM7512AE@TQFP144(7512AE mode) [DX3035]

AMD

E(E)PROM/FRAM/NVRAM

AM25FL005D@SOIC8 [DX1045]
AM25FL010D@SOIC8 [DX1045]
AM25FL016A@SOIC16 [DX1072#1]
AM25FL016A@WSON8 [DX4006#1]
AM25FL020D@SOIC8 [DX1045#1]
AM25FL032A@SOIC16 [DX1072#1]
AM25FL032A@WSON8 [DX4006#1]
AM25FL040D@SOIC8 [DX1045#1]
AM25FL080D@SOIC8 [DX1045#1]
AM27128 [DX0001]
AM27128(DC)@PLCC32 [DX2032]
AM27128A [DX0001]
AM27128A(F)@PLCC32 [DX2032]
AM27128A(PC)@PLCC32 [DX2032]
AM2716 [DX0001]
AM27256 [DX0001]
AM27256AP [DX0001]
AM27256F [DX0001]
AM27256PC [DX0001]
AM2732 [DX0001]
AM2732B [DX0001]
AM27512@PLCC32 [DX2032]
AM27512DC@PLCC32 [DX2032]
AM27512F@PLCC32 [DX2032]
AM27512PC@PLCC32 [DX2032]
AM2764 [DX0001]
AM2764A [DX0001]
AM2764A(DC)@PLCC32 [DX2032]
AM2764A(DI) [DX0001]
AM2764A(F) [DX0001]
AM2764A(JC) [DX0001]
AM2764A(LCB) [DX0001]
AM2764A(LEB) [DX0001]
AM2764A(PC)@PLCC32 [DX2032]
AM27C010 [DX0001]
AM27C010@TSOP32 [DX1002]
AM25FL005D@USON8 [DX4005]
AM25FL010D@USON8 [DX4005]
AM25FL016A@SOIC16(ISP) [DX0001]
AM25FL016A@WSON8(ISP) [DX0001]
AM25FL020D@USON8 [DX4005#1]
AM25FL032A@SOIC16(ISP) [DX0001]
AM25FL032A@WSON8(ISP) [DX0001]
AM25FL040D@USON8 [DX4005#1]
AM25FL080D@USON8 [DX4005#1]
AM27128(DC) [DX0001]
AM27128@PLCC32 [DX2032]
AM27128A(F) [DX0001]
AM27128A(PC) [DX0001]
AM27128A@PLCC32 [DX2032]
AM2716B [DX0001]
AM27256@PLCC32 [DX2032]
AM27256AP@PLCC32 [DX2032]
AM27256F@PLCC32 [DX2032]
AM27256PC@PLCC32 [DX2032]
AM2732A [DX0001]
AM27512 [DX0001]
AM27512DC [DX0001]
AM27512F [DX0001]
AM27512PC [DX0001]
AM27513 [DX0001]
AM2764@PLCC32 [DX2032]
AM2764A(DC) [DX0001]
AM2764A(DCB) [DX0001]
AM2764A(DIB) [DX0001]
AM2764A(F)@PLCC32 [DX2032]
AM2764A(LC) [DX0001]
AM2764A(LE) [DX0001]
AM2764A(PC) [DX0001]
AM2764A@PLCC32 [DX2032]
AM27C010@PLCC32 [DX2032]
AM27C020 [DX0001]

AM27C020@PLCC32 [DX2032]
AM27C020@TSOP32 [DX1002]
AM27C040 [DX0001]
AM27C040@PLCC32 [DX2032]
AM27C040@TSOP32 [DX1002]
AM27C080 [DX0001]
AM27C080@PLCC32 [DX2032]
AM27C080@TSOP32 [DX1002]
AM27C100 [DX0001]
AM27C100@PLCC32 [DX2032]
AM27C100@TSOP32 [DX1002]
AM27C1024 [DX0001]
AM27C1024@PLCC44 [DX2044]
AM27C128 [DX0001]
AM27C128@PLCC32 [DX2032]
AM27C2048 [DX0001]
AM27C2048@PLCC44 [DX2044]
AM27C2048@TSOP40 [DX1006]
AM27C256 [DX0001]
AM27C256(F) [DX0001]
AM27C256(F)@PLCC32 [DX2032]
AM27C256(PC) [DX0001]
AM27C256(PC)@PLCC32 [DX2032]
AM27C256@PLCC32 [DX2032]
AM27C400 [DX0001]
AM27C400@PLCC44 [DX2044]
AM27C4096 [DX0001]
AM27C4096@PLCC44 [DX2044]
AM27C512 [DX0001]
AM27C512(P) [DX0001]
AM27C512(P)@PLCC32 [DX2032]
AM27C512@PLCC32 [DX2032]
AM27C64 [DX0001]
AM27C64@PLCC32 [DX2032]
AM27H010 [DX0001]
AM27H010@PLCC32 [DX2032]
AM27H010@TSOP32 [DX1002]
AM27H256 [DX0001]
AM27H256@PLCC32 [DX2032]
AM27HB010 [DX0001]
AM27HB010@PLCC32 [DX2032]
AM27HB010@TSOP32 [DX1002]
AM27LV010 [DX0001]
AM27LV010@PLCC32 [DX2032]
AM27LV010@TSOP32 [DX1034]
AM27LV010B [DX0001]
AM27LV010B@PLCC32 [DX2032]
AM27LV010B@TSOP32 [DX1002]
AM27LV020 [DX0001]
AM27LV020@PLCC32 [DX2032]
AM27LV020@TSOP32 [DX1002]
AM27LV020B [DX0001]
AM27LV020B@PLCC32 [DX2032]
AM27LV020B@TSOP32 [DX1002]
AM2816A [DX0001]
AM2817A [DX0001]
AM2817A@PLCC32 [DX2032]
AM2817A@SOIC28 [DX1033]
AM2864A [DX0001]
AM2864A(E) [DX0001]
AM2864A(E)@PLCC32 [DX2032]
AM2864A@PLCC32 [DX2032]
AM2864B [DX0001]
AM2864B(E) [DX0001]
AM2864B(E)@PLCC32 [DX2032]
AM2864B@PLCC32 [DX2032]
AM28F001 [DX0001]
AM28F001@PLCC32 [DX2032]
AM28F001@TSOP32 [DX1002]
AM28F010 [DX0001]
AM28F010(REVERSE)@TSOP32 [DX1002]
AM28F010@PLCC32 [DX2032]
AM28F010@TSOP32 [DX1002]
AM28F010A [DX0001]
AM28F010A(REVERSE)@TSOP32 [DX1002]
AM28F010A@PLCC32 [DX2032]
AM28F010A@TSOP32 [DX1002]
AM28F020 [DX0001]
AM28F020(REVERSE)@TSOP32 [DX1002]
AM28F020@PLCC32 [DX2032]
AM28F020@TSOP32 [DX1002]
AM28F020A [DX0001]
AM28F020A(REVERSE)@TSOP32 [DX1002]
AM28F020A@PLCC32 [DX2032]
AM28F020A@TSOP32 [DX1002]
AM28F256 [DX0001]
AM28F256(REVERSE)@TSOP32 [DX1002]

AM28F256@PLCC32 [DX2032]
AM28F256@TSOP32 [DX1002]
AM28F256A [DX0001]
AM28F256A(REVERSE)@TSOP32 [DX1002]
AM28F256A@PLCC32 [DX2032]
AM28F256A@TSOP32 [DX1002]
AM28F512 [DX0001]
AM28F512(REVERSE)@TSOP32 [DX1002]
AM28F512@PLCC32 [DX2032]
AM28F512@TSOP32 [DX1002]
AM28F512A [DX0001]
AM28F512A(REVERSE)@TSOP32 [DX1002]
AM28F512A@PLCC32 [DX2032]
AM28F512A@TSOP32 [DX1002]
AM28F512AF [DX0001]
AM28F512AF(REVERSE)@TSOP32 [DX1002]
AM28F512AF@PLCC32 [DX2032]
AM28F512AF@TSOP32 [DX1002]
AM28F512F [DX0001]
AM28F512F(REVERSE)@TSOP32 [DX1002]
AM28F512F@PLCC32 [DX2032]
AM28F512F@TSOP32 [DX1002]
AM29BDD160GB@FBGA80 [DX5258]
AM29BDD160GB@PQFP80 [DX3020]
AM29BDD160GT@FBGA80 [DX5258]
AM29BDD160GT@PQFP80 [DX3020]
AM29BL162CB@SSOP56 [DX1029]
AM29BL802CB@SSOP56 [DX1029]
AM29DL161DB@FBGA48 [DX5022]
AM29DL161DB@FBGA63 [DX5047]
AM29DL161DB@FBGA64 [DX5074]
AM29DL161DB@TSOP48 [DX1004]
AM29DL161DB@VFBGA48 [DX5043]
AM29DL161DT@FBGA48 [DX5022]
AM29DL161DT@FBGA63 [DX5047]
AM29DL161DT@FBGA64 [DX5074]
AM29DL161DT@TSOP48 [DX1004]
AM29DL161DT@VFBGA48 [DX5043]
AM29DL162CB@FBGA48 [DX5022]
AM29DL162CB@TSOP48 [DX1004]
AM29DL162CT@FBGA48 [DX5022]
AM29DL162CT@TSOP48 [DX1004]
AM29DL162DB@FBGA48 [DX5022]
AM29DL162DB@FBGA63 [DX5047]
AM29DL162DB@FBGA64 [DX5074]
AM29DL162DB@TSOP48 [DX1004]
AM29DL162DB@VFBGA48 [DX5043]
AM29DL162DT@FBGA48 [DX5022]
AM29DL162DT@FBGA63 [DX5047]
AM29DL162DT@FBGA64 [DX5074]
AM29DL162DT@TSOP48 [DX1004]
AM29DL162DT@VFBGA48 [DX5043]
AM29DL163CB@FBGA48 [DX5022]
AM29DL163CB@TSOP48 [DX1004]
AM29DL163CT@FBGA48 [DX5022]
AM29DL163CT@TSOP48 [DX1004]
AM29DL163DB@FBGA48 [DX5022]
AM29DL163DB@FBGA63 [DX5047]
AM29DL163DB@FBGA64 [DX5074]
AM29DL163DB@TSOP48 [DX1004]
AM29DL163DB@VFBGA48 [DX5043]
AM29DL163DT@FBGA48 [DX5022]
AM29DL163DT@FBGA63 [DX5047]
AM29DL163DT@FBGA64 [DX5074]
AM29DL163DT@TSOP48 [DX1004]
AM29DL163DT@VFBGA48 [DX5043]
AM29DL164CB@FBGA48 [DX5022]
AM29DL164CB@TSOP48 [DX1004]
AM29DL164CT@FBGA48 [DX5022]
AM29DL164CT@TSOP48 [DX1004]
AM29DL164DB@FBGA48 [DX5022]
AM29DL164DB@FBGA63 [DX5047]
AM29DL164DB@FBGA64 [DX5074]
AM29DL164DB@TSOP48 [DX1004]
AM29DL164DB@VFBGA48 [DX5043]
AM29DL164DT@FBGA48 [DX5022]
AM29DL164DT@FBGA63 [DX5047]
AM29DL164DT@FBGA64 [DX5074]
AM29DL164DT@TSOP48 [DX1004]
AM29DL164DT@VFBGA48 [DX5043]
AM29DL320GB@FBGA48 [DX5063]
AM29DL320GB@FBGA63 [DX5051]
AM29DL320GB@FBGA64 [DX5074]
AM29DL320GB@TSOP48 [DX1004]
AM29DL320GT@FBGA48 [DX5063]
AM29DL320GT@FBGA63 [DX5051]

AM29DL320GT@FBGA64 [DX5074]
AM29DL320GT@TSOP48 [DX1004]
AM29DL321CB@TSOP48 [DX1004]
AM29DL321CT@TSOP48 [DX1004]
AM29DL322CB@FBGA63 [DX5051]
AM29DL322CB@TSOP48 [DX1004]
AM29DL322CT@FBGA63 [DX5051]
AM29DL322CT@TSOP48 [DX1004]
AM29DL322DB@FBGA63 [DX5051]
AM29DL322DB@TSOP48 [DX1004]
AM29DL322DT@FBGA63 [DX5051]
AM29DL322DT@TSOP48 [DX1004]
AM29DL322GB@FBGA48 [DX5063]
AM29DL322GB@FBGA63 [DX5051]
AM29DL322GB@FBGA64 [DX5074]
AM29DL322GB@TSOP48 [DX1004]
AM29DL322GT@FBGA48 [DX5063]
AM29DL322GT@FBGA63 [DX5051]
AM29DL322GT@FBGA64 [DX5074]
AM29DL322GT@TSOP48 [DX1004]
AM29DL323CB@FBGA63 [DX5051]
AM29DL323CB@TSOP48 [DX1004]
AM29DL323CT@FBGA63 [DX5051]
AM29DL323CT@TSOP48 [DX1004]
AM29DL323DB@FBGA48 [DX5022]
AM29DL323DB@FBGA63 [DX5051]
AM29DL323DB@TSOP48 [DX1004]
AM29DL323DT@FBGA48 [DX5022]
AM29DL323DT@FBGA63 [DX5051]
AM29DL323DT@TSOP48 [DX1004]
AM29DL323GB@FBGA48 [DX5063]
AM29DL323GB@FBGA63 [DX5051]
AM29DL323GB@FBGA64 [DX5074]
AM29DL323GB@TSOP48 [DX1004]
AM29DL323GT@FBGA48 [DX5063]
AM29DL323GT@FBGA63 [DX5051]
AM29DL323GT@FBGA64 [DX5074]
AM29DL323GT@TSOP48 [DX1004]
AM29DL324CB@TSOP48 [DX1004]
AM29DL324CT@TSOP48 [DX1004]
AM29DL324DB@FBGA63 [DX5051]
AM29DL324DB@TSOP48 [DX1004]
AM29DL324DT@FBGA63 [DX5051]
AM29DL324DT@TSOP48 [DX1004]
AM29DL324GB@FBGA48 [DX5063]
AM29DL324GB@FBGA63 [DX5051]
AM29DL324GB@FBGA64 [DX5074]
AM29DL324GB@TSOP48 [DX1004]
AM29DL324GT@FBGA48 [DX5063]
AM29DL324GT@FBGA63 [DX5051]
AM29DL324GT@FBGA64 [DX5074]
AM29DL324GT@TSOP48 [DX1004]
AM29DL400BB(REVERSE)@TSOP48 [DX1004]
AM29DL400BB@PSOP44 [DX1014]
AM29DL400BB@TSOP48 [DX1004]
AM29DL400BT(REVERSE)@TSOP48 [DX1004]
AM29DL400BT@PLCC44 [DX1014]
AM29DL400BT@TSOP48 [DX1004]
AM29DL640D@FBGA63 [DX5041]
AM29DL640D@TSOP48 [DX1004]
AM29DL640G@FBGA63 [DX5041]
AM29DL640G@FBGA64 [DX5074]
AM29DL640G@TSOP48 [DX1004]
AM29DL642G@FBGA63 [DX5041]
AM29DL800B@PSOP44 [DX1014]
AM29DL800B@TSOP48 [DX1004]
AM29DL800BB(REVERSE)@TSOP48 [DX1004]
AM29DL800BB@FBGA48 [DX5039]
AM29DL800BB@PSOP44 [DX1014]
AM29DL800BB@TSOP48 [DX1004]
AM29DL800BT(REVERSE)@TSOP48 [DX1004]
AM29DL800BT@FBGA48 [DX5039]
AM29DL800BT@PSOP44 [DX1014]
AM29DL800BT@TSOP48 [DX1004]
AM29DL800T@PSOP44 [DX1014]
AM29DL800T@TSOP48 [DX1004]
AM29DS163CB@TSOP48 [DX1004]
AM29DS163CT@TSOP48 [DX1004]
AM29DS163DB@FBGA48 [DX5002]
AM29DS163DB@TSOP48 [DX1004]
AM29DS163DT@FBGA48 [DX5002]
AM29DS163DT@TSOP48 [DX1004]
AM29DS323DB@FBGA48 [DX5002]
AM29DS323DB@TSOP48 [DX1004]
AM29DS323DT@FBGA48 [DX5002]
AM29DS323DT@TSOP48 [DX1004]
AM29F002B [DX0001]
AM29F002B@PLCC32 [DX2032]
AM29F002B@TSOP32 [DX1002]
AM29F002BB [DX0001]
AM29F002BB@PLCC32 [DX2032]

AM29F002BB@TSOP32 [DX1002]
AM29F002BT [DX0001]
AM29F002BT@PLCC32 [DX2032]
AM29F002BT@TSOP32 [DX1002]
AM29F002NB [DX0001]
AM29F002NB@PLCC32 [DX2032]
AM29F002NB@TSOP32 [DX1002]
AM29F002NBB [DX0001]
AM29F002NBB@PLCC32 [DX2032]
AM29F002NBB@TSOP32 [DX1002]
AM29F002NBT [DX0001]
AM29F002NBT@PLCC32 [DX2032]
AM29F002NBT@TSOP32 [DX1002]
AM29F002NT [DX0001]
AM29F002NT@PLCC32 [DX2032]
AM29F002NT@TSOP32 [DX1002]
AM29F002T [DX0001]
AM29F002T@PLCC32 [DX2032]
AM29F002T@TSOP32 [DX1002]
AM29F004BB [DX0001]
AM29F004BB@PLCC32 [DX2032]
AM29F004BB@TSOP32 [DX1002]
AM29F004BT [DX0001]
AM29F004BT@PLCC32 [DX2032]
AM29F004BT@TSOP32 [DX1002]
AM29F010 [DX0001]
AM29F010(REVERSE)@TSOP32 [DX1002]
AM29F010@PLCC32 [DX2032]
AM29F010@TSOP32 [DX1002]
AM29F010A [DX0001]
AM29F010A(REVERSE)@TSOP32 [DX1002]
AM29F010A@PLCC32 [DX2032]
AM29F010A@TSOP32 [DX1002]
AM29F010B [DX0001]
AM29F010B(REVERSE)@TSOP32 [DX1002]
AM29F010B@PLCC32 [DX2032]
AM29F010B@TSOP32 [DX1002]
AM29F016@PSOP44 [DX1014]
AM29F016@TSOP40 [DX1006]
AM29F016@TSOP48 [DX1004]
AM29F016B@PSOP44 [DX1014]
AM29F016B@TSOP40 [DX1006]
AM29F016B@TSOP48 [DX1004]
AM29F016D(REVERSE)@TSOP48 [DX1004]
AM29F016D@PSOP44 [DX1014]
AM29F016D@TSOP40 [DX1006]
AM29F016D@TSOP48 [DX1004]
AM29F017B(REVERSE)@TSOP40 [DX1006]
AM29F017B(REVERSE)@TSOP48 [DX1004]
AM29F017B@TSOP40 [DX1006]
AM29F017B@TSOP48 [DX1004]
AM29F017D(REVERSE)@TSOP48 [DX1004]
AM29F017D@TSOP40 [DX1006]
AM29F017D@TSOP48 [DX1004]
AM29F032B@PSOP44 [DX1014]
AM29F032B@TSOP40 [DX1006]
AM29F040 [DX0001]
AM29F040@PLCC32 [DX2032]
AM29F040@TSOP32 [DX1002]
AM29F040A [DX0001]
AM29F040A@PLCC32 [DX2032]
AM29F040A@TSOP32 [DX1002]
AM29F040B [DX0001]
AM29F040B(Reverse)@TSOP32 [DX1002]
AM29F040B@PLCC32 [DX2032]
AM29F040B@TSOP32 [DX1002]
AM29F080(REVERSE)@TSOP40 [DX1006]
AM29F080@PSOP44 [DX1014]
AM29F080@TSOP40 [DX1006]
AM29F080B@PSOP44 [DX1014]
AM29F080B@TSOP40 [DX1006]
AM29F100B(REVERSE)@TSOP48 [DX1004]
AM29F100B@PSOP44 [DX1014]
AM29F100B@TSOP48 [DX1004]
AM29F100T(REVERSE)@TSOP48 [DX1004]
AM29F100T@PSOP44 [DX1014]
AM29F100T@TSOP48 [DX1004]
AM29F160DB(REVERSE)@TSOP48 [DX1004]
AM29F160DB@TSOP48 [DX1004]

AM29F160DT(REVERSE)@TSOP48 [DX1004]
AM29F160DT@TSOP48 [DX1004]
AM29F200AB(REVERSE)@TSOP48 [DX1004]
AM29F200AB@PSOP44 [DX1014]
AM29F200AB@TSOP48 [DX1004]
AM29F200AT(REVERSE)@TSOP48 [DX1004]
AM29F200AT@PSOP44 [DX1014]
AM29F200AT@TSOP48 [DX1004]
AM29F200BB(REVERSE)@TSOP48 [DX1004]
AM29F200BB@PSOP44 [DX1014]
AM29F200BB@TSOP48 [DX1004]
AM29F200BT(REVERSE)@TSOP48 [DX1004]
AM29F200BT@PSOP44 [DX1014]
AM29F200BT@TSOP48 [DX1004]
AM29F400AB(REVERSE)@TSOP48 [DX1004]
AM29F400AB@PSOP44 [DX1014]
AM29F400AB@TSOP48 [DX1004]
AM29F400AT(REVERSE)@TSOP48 [DX1004]
AM29F400AT@PSOP44 [DX1014]
AM29F400AT@TSOP48 [DX1004]
AM29F400BB(REVERSE)@TSOP48 [DX1004]
AM29F400BB@PSOP44 [DX1014]
AM29F400BB@TSOP48 [DX1004]
AM29F400BT(REVERSE)@TSOP48 [DX1004]
AM29F400BT@PSOP44 [DX1014]
AM29F400BT@TSOP48 [DX1004]
AM29F800B(REVERSE)@TSOP48 [DX1004]
AM29F800B@PSOP44 [DX1014]
AM29F800B@TSOP48 [DX1004]
AM29F800BB(REVERSE)@TSOP48 [DX1004]
AM29F800BB@FBGA48 [DX5039]
AM29F800BB@PSOP44 [DX1014]
AM29F800BB@TSOP48 [DX1004]
AM29F800BT(REVERSE)@TSOP48 [DX1004]
AM29F800BT@FBGA48 [DX5039]
AM29F800BT@PSOP44 [DX1014]
AM29F800BT@TSOP48 [DX1004]
AM29F800T(REVERSE)@TSOP48 [DX1004]
AM29F800T@PSOP44 [DX1014]
AM29F800T@TSOP48 [DX1004]
AM29LL800B@TSOP48 [DX1004]
AM29LL800BB@TSOP48 [DX1004]
AM29LL800BT@TSOP48 [DX1004]
AM29LL800T@TSOP48 [DX1004]
AM29LV001BB(REVERSE)@TSOP32 [DX1002]
AM29LV001BB@PLCC32 [DX2032]
AM29LV001BB@TSOP32 [DX1002]
AM29LV001BT(REVERSE)@TSOP32 [DX1002]
AM29LV001BT@PLCC32 [DX2032]
AM29LV001BT@TSOP32 [DX1002]
AM29LV002@TSOP40 [DX1006]
AM29LV002B@TSOP40 [DX1006]
AM29LV002BB@TSOP40 [DX1006]
AM29LV002BT@TSOP40 [DX1006]
AM29LV004B@TSOP40 [DX1006]
AM29LV004BB@TSOP40 [DX1006]
AM29LV004BT@TSOP40 [DX1006]
AM29LV004T@TSOP40 [DX1006]
AM29LV008B@TSOP40 [DX1006]
AM29LV008BB@TSOP40 [DX1006]
AM29LV008BT@TSOP40 [DX1006]
AM29LV008T@TSOP40 [DX1006]
AM29LV010B@PLCC32 [DX2032]
AM29LV010B@TSOP32 [DX1002]
AM29LV017B(REVERSE)@TSOP40 [DX1006]
AM29LV017B@FBGA48 [DX5022]
AM29LV017B@TSOP40 [DX1006]
AM29LV017D(REVERSE)@TSOP40 [DX1006]
AM29LV017D@FBGA48 [DX5022]
AM29LV017D@TSOP40 [DX1006]
AM29LV020B@PLCC32 [DX2032]
AM29LV020B@TSOP32 [DX1002]
AM29LV033C@FBGA63 [DX5051]
AM29LV033C@TSOP40 [DX1006]
AM29LV033MU@FBGA48 [DX5022]
AM29LV033MU@TSOP40 [DX1006]

AM29LV040B@PLCC32 [DX2032]
AM29LV040B@TSOP32 [DX1002]
AM29LV040E@PLCC32 [DX2032]
AM29LV040E@TSOP32 [DX1002]
AM29LV040J@PLCC32 [DX2032]
AM29LV040J@TSOP32 [DX1002]
AM29LV065D@FBGA63 [DX5041]
AM29LV065D@TSOP48 [DX1004]
AM29LV065MU@FBGA63 [DX5041]
AM29LV065MU@TSOP48 [DX1004]
AM29LV080@TSOP40 [DX1006]
AM29LV081@TSOP40 [DX1006]
AM29LV081B@TSOP40 [DX1006]
AM29LV116BB@TSOP40 [DX1006]
AM29LV116BT@TSOP40 [DX1006]
AM29LV116DB@TSOP40 [DX1006]
AM29LV116DT@TSOP40 [DX1006]
AM29LV128MH(REVERSE)@TSOP56 [DX1011]
AM29LV128MH@FBGA64 [DX5074]
AM29LV128MH@TSOP56 [DX1011]
AM29LV128ML(REVERSE)@TSOP56 [DX1011]
AM29LV128ML@FBGA64 [DX5074]
AM29LV128ML@TSOP56 [DX1011]
AM29LV160BB(REVERSE)@TSOP48 [DX1004]
AM29LV160BB@FBGA48 [DX5022]
AM29LV160BB@PSOP44 [DX1014]
AM29LV160BB@TSOP48 [DX1004]
AM29LV160BT(REVERSE)@TSOP48 [DX1004]
AM29LV160BT@FBGA48 [DX5022]
AM29LV160BT@PSOP44 [DX1014]
AM29LV160BT@TSOP48 [DX1004]
AM29LV160DB(REVERSE)@TSOP48 [DX1004]
AM29LV160DB@FBGA48 [DX5022]
AM29LV160DB@PSOP44 [DX1014]
AM29LV160DB@TSOP48 [DX1004]
AM29LV160DT(REVERSE)@TSOP48 [DX1004]
AM29LV160DT@FBGA48 [DX5022]
AM29LV160DT@PSOP44 [DX1014]
AM29LV160DT@TSOP48 [DX1004]
AM29LV160DT@TSOP48(slow) [DX1043]
AM29LV160MB(REVERSE)@TSOP48 [DX1004]
AM29LV160MB@FBGA48 [DX5022]
AM29LV160MB@FBGA64 [DX5074]
AM29LV160MB@PSOP44 [DX1014]
AM29LV160MB@TSOP48 [DX1004]
AM29LV160MT(REVERSE)@TSOP48 [DX1004]
AM29LV160MT@FBGA48 [DX5022]
AM29LV160MT@FBGA64 [DX5074]
AM29LV160MT@PSOP44 [DX1014]
AM29LV160MT@TSOP48 [DX1004]
AM29LV200B(REVERSE)@TSOP48 [DX1004]
AM29LV200B@PSOP44 [DX1014]
AM29LV200B@TSOP48 [DX1004]
AM29LV200BB(REVERSE)@TSOP48 [DX1004]
AM29LV200BB@FBGA48 [DX5002]
AM29LV200BB@PSOP44 [DX1014]
AM29LV200BB@TSOP48 [DX1004]
AM29LV200BT(REVERSE)@TSOP48 [DX1004]
AM29LV200BT@FBGA48 [DX5002]
AM29LV200BT@PSOP44 [DX1014]
AM29LV200BT@TSOP48 [DX1004]
AM29LV200T(REVERSE)@TSOP48 [DX1004]
AM29LV200T@PSOP44 [DX1014]
AM29LV200T@TSOP48 [DX1004]
AM29LV256MH(REVERSE)@TSOP56 [DX1011]
AM29LV256MH@FBGA64 [DX5075]
AM29LV256MH@TSOP56 [DX1011]
AM29LV256ML(REVERSE)@TSOP56 [DX1011]
AM29LV256ML@FBGA64 [DX5075]
AM29LV256ML@TSOP56 [DX1011]
AM29LV320DB@FBGA48 [DX5040]
AM29LV320DB@TSOP48 [DX1004]
AM29LV320DT@FBGA48 [DX5040]
AM29LV320DT@TSOP48 [DX1004]

AM29LV320FB@TSOP48 [DX1004]
AM29LV320FT@TSOP48 [DX1004]
AM29LV320MB@FBGA48 [DX5022]
AM29LV320MB@FBGA64 [DX5074]
AM29LV320MB@TSOP48 [DX1004]
AM29LV320MH(REVERSE)@TSOP56 [DX1011]
AM29LV320MH@FBGA64 [DX5074]
AM29LV320MH@TSOP56 [DX1011]
AM29LV320ML(REVERSE)@TSOP56 [DX1011]
AM29LV320ML@FBGA64 [DX5074]
AM29LV320ML@TSOP56 [DX1011]
AM29LV320MT@FBGA48 [DX5022]
AM29LV320MT@FBGA64 [DX5074]
AM29LV320MT@TSOP48 [DX1004]
AM29LV400B(REVERSE)@TSOP48 [DX1004]
AM29LV400B@FBGA48 [DX5002]
AM29LV400B@PSOP44 [DX1014]
AM29LV400B@TSOP48 [DX1004]
AM29LV400BB(REVERSE)@TSOP48 [DX1004]
AM29LV400BB@FBGA48 [DX5002]
AM29LV400BB@PSOP44 [DX1014]
AM29LV400BB@TSOP48 [DX1004]
AM29LV400BT(REVERSE)@TSOP48 [DX1004]
AM29LV400BT@FBGA48 [DX5002]
AM29LV400BT@PSOP44 [DX1014]
AM29LV400BT@TSOP48 [DX1004]
AM29LV400T(REVERSE)@TSOP48 [DX1004]
AM29LV400T@FBGA48 [DX5002]
AM29LV400T@PSOP44 [DX1014]
AM29LV400T@TSOP48 [DX1004]
AM29LV640DH@SSOP56 [DX1029]
AM29LV640DL@SSOP56 [DX1029]
AM29LV640DU@FBGA63 [DX5041]
AM29LV640DU@FBGA64 [DX5074]
AM29LV640GU@FBGA63 [DX5041]
AM29LV640GU@FBGA64 [DX5074]
AM29LV640MB@FBGA63 [DX5041]
AM29LV640MB@FBGA64 [DX5074]
AM29LV640MB@TSOP48 [DX1004]
AM29LV640MH(REVERSE)@TSOP56 [DX1011]
AM29LV640MH@FBGA64 [DX5074]
AM29LV640MH@TSOP56 [DX1011]
AM29LV640ML(REVERSE)@TSOP56 [DX1011]
AM29LV640ML@FBGA64 [DX5074]
AM29LV640ML@TSOP56 [DX1011]
AM29LV640MT@FBGA63 [DX5041]
AM29LV640MT@FBGA64 [DX5074]
AM29LV640MT@TSOP48 [DX1004]
AM29LV640MU@FBGA63 [DX5041]
AM29LV640MU@FBGA64 [DX5074]
AM29LV641DH(REVERSE)@TSOP48 [DX1004]
AM29LV641DH@TSOP48 [DX1004]
AM29LV641DL(REVERSE)@TSOP48 [DX1004]
AM29LV641DL@TSOP48 [DX1004]
AM29LV641GH(REVERSE)@TSOP48 [DX1004]
AM29LV641GH@TSOP48 [DX1004]
AM29LV641GL(REVERSE)@TSOP48 [DX1004]
AM29LV641GL@TSOP48 [DX1004]
AM29LV641MH(REVERSE)@TSOP48 [DX1004]
AM29LV641MH@TSOP48 [DX1004]
AM29LV641ML(REVERSE)@TSOP48 [DX1004]
AM29LV641ML@TSOP48 [DX1004]
AM29LV642D@FBGA64 [DX5074]
AM29LV642G@FBGA64 [DX5074]
AM29LV652D@FBGA63 [DX5041]
AM29LV800B(REVERSE)@TSOP48 [DX1004]
AM29LV800B@PSOP44 [DX1014]
AM29LV800B@TSOP48 [DX1004]
AM29LV800BB(REVERSE)@TSOP48 [DX1004]

AM29LV800BB@FBGA48 [DX5039]　　AM29LV800BB@PSOP44 [DX1014]
AM29LV800BB@TSOP48 [DX1004]
AM29LV800BT(REVERSE)@TSOP48 [DX1004]
AM29LV800BT@FBGA48 [DX5039]　　AM29LV800BT@PSOP44 [DX1014]
AM29LV800BT@TSOP48 [DX1004]
AM29LV800DB(REVERSE)@TSOP48 [DX1004]
AM29LV800DB(WB)@FBGA48 [DX5039]　　AM29LV800DB(WC)@FBGA48 [DX5043]
AM29LV800DB@PSOP44 [DX1014]　　AM29LV800DB@TSOP48 [DX1004]
AM29LV800DT(REVERSE)@TSOP48 [DX1004]
AM29LV800DT(WB)@FBGA48 [DX5039]　　AM29LV800DT(WC)@FBGA48 [DX5043]
AM29LV800DT@PSOP44 [DX1014]　　AM29LV800DT@TSOP48 [DX1004]
AM29LV800T(REVERSE)@TSOP48 [DX1004]
AM29LV800T@PSOP44 [DX1014]　　AM29LV800T@TSOP48 [DX1004]
AM29PDL128G70(REVERSE)@FBGA80 [DX5147]
AM29PDL128G70@FBGA80 [DX5147]　　AM29PDL128G80@FBGA80 [DX5147]
AM29PDL128G90@FBGA80 [DX5147]　　AM29PDS322DB@FBGA48 [DX50UN]
AM29PDS322DT@FBGA48 [DX50UN]　　AM29PL160BB@PSOP44 [DX1014]
AM29PL160BB@TSOP48 [DX1004]　　AM29PL160CB@PSOP44 [DX1014]
AM29PL160CB@TSOP48 [DX1004]　　AM29PL160CT@PSOP44 [DX1014]
AM29PL160CT@TSOP48 [DX1004]　　AM29SL160BB@FBGA48 [DX5022]
AM29SL160BB@TSOP48 [DX1004]　　AM29SL160BT@FBGA48 [DX5022]
AM29SL160BT@TSOP48 [DX1004]　　AM29SL160CB@FBGA48 [DX5022]
AM29SL160CB@TSOP48 [DX1004]　　AM29SL160CT@FBGA48 [DX5022]
AM29SL160CT@TSOP48 [DX1004]　　AM29SL400CB@FBGA48 [DX5002]
AM29SL400CB@TSOP48 [DX1004]　　AM29SL400CT@FBGA48 [DX5002]
AM29SL400CT@TSOP48 [DX1004]
AM29SL800BB(REVERSE)@TSOP48 [DX1004]
AM29SL800BB@FBGA48 [DX5039]　　AM29SL800BB@TSOP48 [DX1004]
AM29SL800BT(REVERSE)@TSOP48 [DX1004]
AM29SL800BT@FBGA48 [DX5039]　　AM29SL800BT@TSOP48 [DX1004]
AM29SL800CB(REVERSE)@TSOP48 [DX1004]
AM29SL800CB@FBGA48 [DX5039]　　AM29SL800CB@TSOP48 [DX1004]
AM29SL800CT(REVERSE)@TSOP48 [DX1004]
AM29SL800CT@FBGA48 [DX5039]　　AM29SL800CT@TSOP48 [DX1004]
AM29SL800DB(REVERSE)@TSOP48 [DX1004]
AM29SL800DB@TSOP48 [DX1004]　　AM29SL800DBUF@FBGA48 [DX5038]
AM29SL800DBVG@FBGA48 [DX5038]　　AM29SL800DBVU@FBGA48 [DX5043]
AM29SL800DBWA@FBGA48 [DX5002]　　AM29SL800DBWC@FBGA48 [DX5022]
AM29SL800DT(REVERSE)@TSOP48 [DX1004]
AM29SL800DT@TSOP48 [DX1004]　　AM29SL800DTUF@FBGA48 [DX5038]
AM29SL800DTVG@FBGA48 [DX5038]　　AM29SL800DTVU@FBGA48 [DX5043]
AM29SL800DTWA@FBGA48 [DX5002]　　AM29SL800DTWC@FBGA48 [DX5022]
AM30LV0064DJ40@TSOP44 [DX1046]　　AM9716 [DX0001]
AM9732 [DX0001]　　AM9732A [DX0001]
AM9764 [DX0001]　　AM9764@PLCC32 [DX2032]
AT29BDS640GB73@FBGA64 [DX50UN]　　AT29BDS640GB74@FBGA64 [DX50UN]
AT29BDS640GB78@FBGA64 [DX50UN]　　AT29BDS640GB79@FBGA64 [DX50UN]
AT29BDS640GB93@FBGA64 [DX50UN]　　AT29BDS640GB94@FBGA64 [DX50UN]

AT29BDS640GB98@FBGA64 [DX50UN]　　AT29BDS640GB99@FBGA64 [DX50UN]
AT29BDS640GT73@FBGA64 [DX50UN]　　AT29BDS640GT74@FBGA64 [DX50UN]
AT29BDS640GT78@FBGA64 [DX50UN]　　AT29BDS640GT79@FBGA64 [DX50UN]
AT29BDS640GT93@FBGA64 [DX50UN]　　AT29BDS640GT94@FBGA64 [DX50UN]
AT29BDS640GT98@FBGA64 [DX50UN]　　AT29BDS640GT99@FBGA64 [DX50UN]
BS128HD5V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD6V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD8V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD9V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HE5V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE6V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE8V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE9V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HF5V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF6V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF8V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF9V(AM29BDS128HF)@FBGA80 [DX5053]
BS640HD8V(AM29BDS640HD)@FBGA64 [DX5053]
BS640HD9V(AM29BDS640HD)@FBGA64 [DX5053]
BS640HE8V(AM29BDS640HE)@FBGA64 [DX5053]
BS640HE9V(AM29BDS640HE)@FBGA64 [DX5053]
BS640HF8V(AM29BDS640HF)@FBGA64 [DX5053]
BS640HF9V(AM29BDS640HF)@FBGA64 [DX5053]
DS42514(AM29DL1634DB)@FBGA69 [DX5001]
DS42515(AM29DL1644DB)@FBGA69 [DX5001]
DS42516(AM29DL324DB)@FBGA73 [DX5001]
DS42546(AM29DL1634DT)@FBGA69 [DX5001]
DS42553(AM29DL323DT)@FBGA73 [DX5001]
DS42585(AM29DL323DT)@FBGA73 [DX5001]
DS42587(AM29DL324DB)@FBGA73 [DX5001]
DS42629(AM29DL640G)@VFBGA48 [DX5080]
DS42677(AM29LV128MH/L)@FBGA88 [DX5053]
DS42678(AM29LV320MT)@FBGA67 [DX5001]
DS42689(AM29LV320MT)@FBGA64 [DX5004]
DS42690(AM29LV320MB)@FBGA64 [DX5004]
DS42695(AM29LV320MT)@FBGA64 [DX5074]
DS42696(AM29LV320MB)@FBGA64 [DX5074]
DS42701(AM29LV640MU)@FBGA88 [DX5053]
DS42725(AM50DL128CH)@FBGA88 [DX5001]
DS42772A(AM29LV640M)@FBGA88 [DX5053]
M410000000(AM41DL1614DT)@FBGA69 [DX5001]
M410000001(AM41DL1614DB)@FBGA69 [DX5001]
M410000002(AM41DL1614DT)@FBGA69 [DX5001]
M410000003(AM41DL1614DB)@FBGA69 [DX5001]
M410000004(AM41DL1624DT)@FBGA69 [DX5001]
M410000005(AM41DL1624DB)@FBGA69 [DX5001]
M410000006(AM41DL1624DT)@FBGA69 [DX5001]
M410000007(AM41DL1624DB)@FBGA69 [DX5001]

M410000008(AM41DL1634DT)@FBGA69 [DX5001]
M410000009(AM41DL1634DB)@FBGA69 [DX5001]
M41000000A(AM41DL1634DT)@FBGA69 [DX5001]
M41000000B(AM41DL1634DB)@FBGA69 [DX5001]
M41000000C(AM41DL1644DT)@FBGA69 [DX5001]
M41000000D(AM41DL1644DB)@FBGA69 [DX5001]
M41000000E(AM41DL1644DT)@FBGA69 [DX5001]
M41000000F(AM41DL1644DB)@FBGA69 [DX5001]
M41000000G(AM41DL6408G)@FBGA73 [DX5001]
M41000000H(AM41DL6408G)@FBGA73 [DX5001]
M41000001W(AM41DL3224GT)@FBGA73 [DX5001]
M41000001X(AM41DL3224GB)@FBGA73 [DX5001]
M41000001Y(AM41DL3224GT)@FBGA73 [DX5001]
M41000001Z(AM41DL3224GB)@FBGA73 [DX5001]
M410000020(AM41DL3234GT)@FBGA73 [DX5001]
M410000021(AM41DL3234GB)@FBGA73 [DX5001]
M410000022(AM41DL3234GT)@FBGA73 [DX5001]
M410000023(AM41DL3234GB)@FBGA73 [DX5001]
M410000024(AM41DL3244GT)@FBGA73 [DX5001]
M410000025(AM41DL3244GB)@FBGA73 [DX5001]
M410000026(AM41DL3244GT)@FBGA73 [DX5001]
M410000027(AM41DL3244GB)@FBGA73 [DX5001]
M41000002L(AM41DL3228GT)@FBGA73 [DX5001]
M41000002M(AM41DL3228GB)@FBGA73 [DX5001]
M41000002N(AM41DL3228GT)@FBGA73 [DX5001]
M41000002O(AM41DL3228GB)@FBGA73 [DX5001]
M41000002P(AM41DL3238GT)@FBGA73 [DX5001]
M41000002Q(AM41DL3238GB)@FBGA73 [DX5001]
M41000002R(AM41DL3238GT)@FBGA73 [DX5001]
M41000002S(AM41DL3238GB)@FBGA73 [DX5001]
M41000002T(AM41DL3248GT)@FBGA73 [DX5001]
M41000002U(AM41DL3248GB)@FBGA73 [DX5001]
M41000002V(AM41DL3248GT)@FBGA73 [DX5001]
M41000002W(AM41DL3248GB)@FBGA73 [DX5001]
M41000003D(AM41DL3208GT)@FBGA73 [DX5001]
M41000003E(AM41DL3208GB)@FBGA73 [DX5001]
M41000003F(AM41DL3208GT)@FBGA73 [DX5001]
M41000003G(AM41DL3208GB)@FBGA73 [DX5001]
M410000095(AM41LV3204MT)@FBGA69 [DX5005]
M410000096(AM41LV3204MB)@FBGA69 [DX5005]
M41000009B(AM41DL6408H)@FBGA73 [DX5001]
M41000009C(AM41DL6408H)@FBGA73 [DX5001]
M41000009D(AM41DL6408H)@FBGA73 [DX5001]
M420000000(AM42DL640AG)@FBGA73 [DX5001]
M420000001(AM42DL640AG)@FBGA73 [DX5001]
M420000004(AM42DL1642DT)@FBGA69 [DX5001]
M420000005(AM42DL1642DB)@FBGA69 [DX5001]
M420000006(AM42DL1642DT)@FBGA69 [DX5001]

M420000007(AM42DL1642DB)@FBGA69 [DX5001]
M42000000I(AM42DL1612DT)@FBGA69 [DX5001]
M42000000J(AM42DL1612DB)@FBGA69 [DX5001]
M42000000K(AM42DL1612DT)@FBGA69 [DX5001]
M42000000L(AM42DL1612DB)@FBGA69 [DX5001]
M42000000M(AM42DL1622DT)@FBGA69 [DX5001]
M42000000N(AM42DL1622DB)@FBGA69 [DX5001]
M420000000(AM42DL1622DT)@FBGA69 [DX5001]
M42000000P(AM42DL1622DB)@FBGA69 [DX5001]
M42000000Q(AM42DL1632DT)@FBGA69 [DX5001]
M42000000R(AM42DL1632DB)@FBGA69 [DX5001]
M42000000S(AM42DL1632DT)@FBGA69 [DX5001]
M42000000T(AM42DL1632DB)@FBGA69 [DX5001]
M42000000U(AM42DL1642DT)@FBGA69 [DX5001]
M42000000V(AM42DL1642DB)@FBGA69 [DX5001]
M42000000W(AM42DL1642DT)@FBGA69 [DX5001]
M42000000X(AM42DL1642DB)@FBGA69 [DX5001]
M42000001A(AM42DL1614DT)@FBGA69 [DX5001]
M42000001B(AM42DL1614DB)@FBGA69 [DX5001]
M42000001C(AM42DL1614DT)@FBGA69 [DX5001]
M42000001D(AM42DL1614DB)@FBGA69 [DX5001]
M42000001E(AM42DL1624DT)@FBGA69 [DX5001]
M42000001F(AM42DL1624DB)@FBGA69 [DX5001]
M42000001G(AM42DL1624DT)@FBGA69 [DX5001]
M42000001H(AM42DL1624DB)@FBGA69 [DX5001]
M42000001I(AM42DL1634DT)@FBGA69 [DX5001]
M42000001J(AM42DL1634DB)@FBGA69 [DX5001]
M42000001K(AM42DL1634DT)@FBGA69 [DX5001]
M42000001L(AM42DL1634DB)@FBGA69 [DX5001]
M42000001M(AM42DL1644DT)@FBGA69 [DX5001]
M42000001N(AM42DL1644DB)@FBGA69 [DX5001]
M42000001O(AM42DL1644DT)@FBGA69 [DX5001]
M42000001P(AM42DL1644DB)@FBGA69 [DX5001]
M420000022(AM42DL3224GT)@FBGA73 [DX5001]
M420000023(AM42DL3224GB)@FBGA73 [DX5001]
M420000024(AM42DL3224GT)@FBGA73 [DX5001]
M420000025(AM42DL3224GB)@FBGA73 [DX5001]
M420000026(AM42DL3234GT)@FBGA73 [DX5001]
M420000027(AM42DL3234GB)@FBGA73 [DX5001]
M420000028(AM42DL3234GT)@FBGA73 [DX5001]
M420000029(AM42DL3234GB)@FBGA73 [DX5001]
M42000002A(AM42DL3244GT)@FBGA73 [DX5001]
M42000002B(AM42DL3244GB)@FBGA73 [DX5001]
M42000002C(AM42DL3244GT)@FBGA73 [DX5001]
M42000002D(AM42DL3244GB)@FBGA73 [DX5001]
M42000002U(AM42DL6404G)@FBGA73 [DX5001]
M42000002V(AM42DL6404G)@FBGA73 [DX5001]
M42000002Y(AM42BDS6408GT)@FBGA93 [DX5001]

M420000002Z(AM42BDS6408GB)@FBGA93 [DX5001]
M420000030(AM42BDS6408GT)@FBGA93 [DX5001]
M420000031(AM42BDS6408GB)@FBGA93 [DX5001]
M420000032(AM42BDS6408GT)@FBGA93 [DX5001]
M420000033(AM42BDS6408GB)@FBGA93 [DX5001]
M420000034(AM42BDS6408GT)@FBGA93 [DX5001]
M420000035(AM42BDS6408GB)@FBGA93 [DX5001]
M42000004Y(AM42BDS640AGT)@FBGA93 [DX5001]
M42000004Z(AM42BDS640AGB)@FBGA93 [DX5001]
M420000050(AM42BDS640AGT)@FBGA93 [DX5001]
M420000051(AM42BDS640AGB)@FBGA93 [DX5001]
M420000052(AM42BDS640AGT)@FBGA93 [DX5001]
M420000053(AM42BDS640AGB)@FBGA93 [DX5001]
M420000054(AM42BDS640AGT)@FBGA93 [DX5001]
M420000055(AM42BDS640AGB)@FBGA93 [DX5001]
M42000005M(AM42DL6402G)@FBGA73 [DX5001]
M42000005N(AM42DL6402G)@FBGA73 [DX5001]
M42000005W(AM42DL3224GT)@FBGA73 [DX5001]
M42000005X(AM42DL3224GB)@FBGA73 [DX5001]
M42000005Y(AM42DL3234GT)@FBGA73 [DX5001]
M42000005Z(AM42DL3234GB)@FBGA73 [DX5001]
M420000060(AM42DL3244GT)@FBGA73 [DX5001]
M420000061(AM42DL3244GB)@FBGA73 [DX5001]
M420000070(AM42BDS6408HE8)@BGA89 [DX5005]
M420000071(AM42BDS6408HE9)@BGA89 [DX5005]
M420000072(AM42BDS6408HD8)@BGA89 [DX5005]
M420000073(AM42BDS6408HD9)@BGA89 [DX5005]
M420000074(AM42BDS6408HE3)@BGA89 [DX5005]
M420000075(AM42BDS6408HE4)@BGA89 [DX5005]
M420000076(AM42BDS6408HD3)@BGA89 [DX5005]
M420000077(AM42BDS6408HD4)@BGA89 [DX5005]
M420000078(AM42DL640AH)@FBGA73 [DX5001]
M420000079(AM42DL640AH)@FBGA73 [DX5001]
M450000000(AM45DL6408G)@FBGA73 [DX5001]
M450000001(AM45DL6408G)@FBGA73 [DX5001]
M450000008(AM45DL3208GT)@FBGA73 [DX5001]
M450000009(AM45DL3208GB)@FBGA73 [DX5001]
M45000000A(AM45DL3208GT)@FBGA73 [DX5001]
M45000000B(AM45DL3208GB)@FBGA73 [DX5001]
M45000000S(AM45DL3228GT)@FBGA73 [DX5001]
M45000000T(AM45DL3228GB)@FBGA73 [DX5001]
M45000000U(AM45DL3228GT)@FBGA73 [DX5001]
M45000000V(AM45DL3228GB)@FBGA73 [DX5001]
M45000001C(AM45DL3238GT)@FBGA73 [DX5001]
M45000001D(AM45DL3238GB)@FBGA73 [DX5001]
M45000001E(AM45DL3238GT)@FBGA73 [DX5001]
M45000001F(AM45DL3238GB)@FBGA73 [DX5001]
M45000001W(AM45DL3248GT)@FBGA73 [DX5001]

M45000001X(AM45DL3248GB)@FBGA73 [DX5001]
M45000001Y(AM45DL3248GT)@FBGA73 [DX5001]
M45000001Z(AM45DL3248GB)@FBGA73 [DX5001]
M490000000(AM49DL640BG)@FBGA73 [DX5001]
M490000001(AM49DL640BG)@FBGA73 [DX5001]
M49000000G(AM49DL320BGT)@FBGA73 [DX5001]
M49000000H(AM49DL320BGT)@FBGA73 [DX5001]
M49000000J(AM49DL322BGT)@FBGA73 [DX5001]
M49000000K(AM49DL322BGT)@FBGA73 [DX5001]
M49000000L(AM49DL322BGB)@FBGA73 [DX5001]
M49000000M(AM49DL322BGB)@FBGA73 [DX5001]
M49000000N(AM49DL323BGT)@FBGA73 [DX5001]
M490000000(AM49DL323BGT)@FBGA73 [DX5001]
M49000000P(AM49DL323BGB)@FBGA73 [DX5001]
M49000000Q(AM49DL323BGB)@FBGA73 [DX5001]
M49000000R(AM49DL324BGT)@FBGA73 [DX5001]
M49000000S(AM49DL324BGT)@FBGA73 [DX5001]
M49000000T(AM49DL324BGB)@FBGA73 [DX5001]
M49000000U(AM49DL324BGB)@FBGA73 [DX5001]
M49000001A(AM49DL320BGB)@FBGA73 [DX5001]
M49000001B(AM49DL320BGB)@FBGA73 [DX5001]
M49000001Y(AM49PDL640AG)@FBGA73 [DX5072]
M49000001Z(AM49PDL640AG)@FBGA73 [DX5072]
M490000025(AM49DL640AG)@FBGA73 [DX5001]
M490000026(AM49DL640AG)@FBGA73 [DX5001]
M490000028(AM49PDL127BH)@FBGA73 [DX5001]
M490000029(AM49PDL127BH)@FBGA73 [DX5001]
M49000002I(AM49PDL127AH)@FBGA73 [DX5001]
M49000002J(AM49PDL127AH)@FBGA73 [DX5001]
M49000002T(AM49LV6408MT)@FBGA69 [DX5005]
M49000002U(AM49LV6408MB)@FBGA69 [DX5005]
M49000002V(AM49LV6408MT)@FBGA69 [DX5005]
M49000002X(AM49LV6408MB)@FBGA69 [DX5005]
M490000030(AM49PDL129BH)@FBGA73 [DX5001]
M490000031(AM49PDL129BH)@FBGA73 [DX5001]
M490000032(AM49DL3208GB)@FBGA69 [DX5001]
M490000032(AM49DL3208GT)@FBGA69 [DX5005]
M490000034(AM49DL3208GT)@FBGA69 [DX5005]
M490000035(AM49DL3208GB)@FBGA69 [DX5001]
M49000003A(AM49DL640BH)@FBGA73 [DX5001]
M49000003B(AM49DL640BH)@FBGA73 [DX5001]
M49000003C(AM49DL640BH)@FBGA73 [DX5001]
M49000003D(AM49DL640AH)@FBGA73 [DX5001]
M49000003E(AM49DL640AH)@FBGA73 [DX5001]
M49000003F(AM49DL6408H)@FBGA73 [DX5001]
M49000003G(AM49DL6408H)@FBGA73 [DX5001]
M49000003H(AM49DL6408H)@FBGA73 [DX5001]
M49000003I(AM49DL6408H)@FBGA73 [DX5001]

M49000003J(AM49DL640AH)@FBGA73 [DX5001]
M49000003X(AM49DL6408H)@FBGA73 [DX5001]
M49000003Y(AM49DL6408H)@FBGA73 [DX5001]
M49000003Z(AM49LV6408MT)@FBGA69 [DX5005]
M49000004A(AM49LV6408MB)@FBGA69 [DX5005]
M49000004B(AM49BDS640AH)@FBGA89 [DX5005]
M49000004C(AM49BDS640AH)@FBGA89 [DX5005]
M49000004D(AM49BDS640AH)@FBGA89 [DX5005]
M49000004E(AM49BDS640AH)@FBGA89 [DX5005]
M49000004H(AM49LV128BMH)@FBGA64 [DX5054]
M49000004J(AM49LV128BML)@FBGA64 [DX5054]
M49000004K(AM49LV128BMH)@FBGA64 [DX5054]
M49000004L(AM49LV128BML)@FBGA64 [DX5054]
M49000004S(AM49LV128BMaH)@FBGA64 [DX5054]
M49000004T(AM49LV128BMaL)@FBGA64 [DX5054]
M49000004U(AM49LV128BMaH)@FBGA64 [DX5054]
M49000004V(AM49LV128BMaL)@FBGA64 [DX5054]
M4900000K(AM49PDL129AH)@FBGA73 [DX5001]
M4900000L(AM49PDL129AH)@FBGA73 [DX5001]
M500000000(AM50DL128BG)@FBGA73 [DX5001]
M500000001(AM50DL128BG)@FBGA73 [DX5001]
M500000008(AM50DL128CG)@FBGA88 [DX5001]
M500000009(AM50DL128CG)@FBGA88 [DX5001]
M50000004J(AM50DL128BH)@FBGA73 [DX5001]
M50000004K(AM50DL128BH)@FBGA73 [DX5001]
M50000004L(AM50DL128BH)@FBGA73 [DX5001]
M50000004M(AM50DL128CH)@FBGA88 [DX5001]
M50000004N(AM50DL128CH)@FBGA88 [DX5001]
M50000004P(AM50DL128CH)@FBGA88 [DX5001]
M550000000(AM55DL128C8G)@FBGA93 [DX5028]
M550000001(AM55DL128C8G)@FBGA93 [DX5028]
PDL127H53V(AM29PDL127H53)@FBGA80 [DX5053]
PDL127H63V(AM29PDL127H63)@FBGA80 [DX5053]
PDL127H68V(AM29PDL127H68)@FBGA80 [DX5053]
PDL127H88V(AM29PDL127H88)@FBGA80 [DX5053]
PDL129H53V(AM29PDL129H53)@FBGA80 [DX5053]
PDL129H63V(AM29PDL129H63)@FBGA80 [DX5053]
PDL129H68V(AM29PDL129H68)@FBGA80 [DX5053]
PDL129H88V(AM29PDL129H88)@FBGA80 [DX5053]

BPROM

AM27LS19 [DX0001]
AM27LS19@PLCC20 [DX2020]
AM27LS19@SOIC16 [DX1033]
AM27PS191 [DX0001]
AM27PS191@PLCC28 [DX2028]
AM27PS191@PLCC32 [DX2032]
AM27PS191@SOIC24 [DX0133]
AM27PS191A [DX0001]
AM27PS191A@PLCC28 [DX2028]
AM27PS191A@PLCC32 [DX2032]

AM27PS191A@SOIC24 [DX0133]
AM27PS291 [DX0001]
AM27PS291@PLCC28 [DX2028]
AM27PS291@PLCC32 [DX2032]
AM27PS291@SOIC24 [DX0133]
AM27PS291A [DX0001]
AM27PS291A@PLCC28 [DX2028]
AM27PS291A@PLCC32 [DX2032]
AM27PS291A@SOIC24 [DX0133]
AM27PS41 [DX0001]
AM27PS41@PLCC28 [DX2028]
AM27PS41@SOIC20 [DX1033]
AM27S13 [DX0001]
AM27S13@PLCC20 [DX2020]
AM27S13@SOIC16 [DX1033]
AM27S13A [DX0001]
AM27S13A@PLCC20 [DX2020]
AM27S13A@SOIC16 [DX1033]
AM27S18 [DX0001]
AM27S18@PLCC20 [DX2020]
AM27S18@SOIC16 [DX1033]
AM27S180 [DX0001]
AM27S180@PLCC28 [DX2028]
AM27S180@PLCC32 [DX2032]
AM27S180@SOIC24 [DX0133]
AM27S180A [DX0001]
AM27S180A@PLCC28 [DX2028]
AM27S180A@PLCC32 [DX2032]
AM27S180A@SOIC24 [DX0133]
AM27S181 [DX0001]
AM27S181@PLCC28 [DX2028]
AM27S181@PLCC32 [DX2032]
AM27S181@SOIC24 [DX0133]
AM27S181A [DX0001]
AM27S181A@PLCC28 [DX2028]
AM27S181A@PLCC32 [DX2032]
AM27S181A@SOIC24 [DX0133]
AM27S184 [DX0001]
AM27S184@PLCC28 [DX2028]
AM27S184@SOIC18 [DX1033]
AM27S185 [DX0001]
AM27S185@PLCC28 [DX2028]
AM27S185@SOIC18 [DX1033]
AM27S185A [DX0001]
AM27S185A@PLCC28 [DX2028]
AM27S185A@SOIC18 [DX1033]
AM27S18A [DX0001]
AM27S18A@PLCC20 [DX2020]
AM27S18A@SOIC16 [DX1033]
AM27S19 [DX0001]
AM27S19@PLCC20 [DX2020]
AM27S19@SOIC16 [DX1033]
AM27S190 [DX0001]
AM27S190@PLCC28 [DX2028]
AM27S190@PLCC32 [DX2032]
AM27S190@SOIC24 [DX0133]
AM27S190A [DX0001]
AM27S190A@PLCC28 [DX2028]
AM27S190A@PLCC32 [DX2032]
AM27S190A@SOIC24 [DX0133]
AM27S191 [DX0001]
AM27S191@PLCC28 [DX2028]
AM27S191@PLCC32 [DX2032]
AM27S191@SOIC24 [DX0133]
AM27S191A [DX0001]
AM27S191A@PLCC28 [DX2028]
AM27S191A@PLCC32 [DX2032]
AM27S191A@SOIC24 [DX0133]
AM27S191SA [DX0001]
AM27S191SA@PLCC28 [DX2028]
AM27S191SA@PLCC32 [DX2032]
AM27S191SA@SOIC24 [DX0133]
AM27S19A [DX0001]
AM27S19A@PLCC20 [DX2020]
AM27S19A@SOIC16 [DX1033]
AM27S19SA [DX0001]
AM27S19SA@PLCC20 [DX2020]
AM27S19SA@SOIC16 [DX1033]
AM27S20 [DX0001]
AM27S20@PLCC20 [DX2020]
AM27S20@SOIC16 [DX1033]
AM27S21 [DX0001]
AM27S21@PLCC20 [DX2020]
AM27S21@SOIC16 [DX1033]
AM27S21A [DX0001]
AM27S21A@PLCC20 [DX2020]
AM27S21A@SOIC16 [DX1033]
AM27S23 [DX0001]
AM27S23@PLCC20 [DX2020]
AM27S23@SOIC20 [DX1033]
AM27S23A [DX0001]
AM27S23A@PLCC20 [DX2020]
AM27S23A@SOIC20 [DX1033]
AM27S25 [DX0001]
AM27S25@PLCC28 [DX2028]
AM27S25@PLCC32 [DX2032]

AM27S25@SOIC24 [DX1033]
AM27S25A [DX0001]
AM27S25A@PLCC28 [DX2028]
AM27S25A@PLCC32 [DX2032]
AM27S25A@SOIC24 [DX1033]
AM27S25SA [DX0001]
AM27S25SA@PLCC28 [DX2028]
AM27S25SA@PLCC32 [DX2032]
AM27S25SA@SOIC24 [DX1033]
AM27S27 [DX0001]
AM27S27@SOIC24 [DX1033]
AM27S27A [DX0001]
AM27S27A@SOIC24 [DX1033]
AM27S280 [DX0001]
AM27S280@PLCC28 [DX2028]
AM27S280@PLCC32 [DX2032]
AM27S280@SOIC24 [DX0133]
AM27S281 [DX0001]
AM27S281@PLCC28 [DX2028]
AM27S281@PLCC32 [DX2032]
AM27S281@SOIC24 [DX0133]
AM27S281A [DX0001]
AM27S281A@PLCC28 [DX2028]
AM27S281A@PLCC32 [DX2032]
AM27S281A@SOIC24 [DX0133]
AM27S29 [DX0001]
AM27S29@PLCC20 [DX2020]
AM27S29@SOIC20 [DX1033]
AM27S291 [DX0001]
AM27S291@PLCC28 [DX2028]
AM27S291@PLCC32 [DX2032]
AM27S291@SOIC24 [DX0133]
AM27S291A [DX0001]
AM27S291A@PLCC28 [DX2028]
AM27S291A@PLCC32 [DX2032]
AM27S291A@SOIC24 [DX0133]
AM27S291SA [DX0001]
AM27S291SA@PLCC28 [DX2028]
AM27S291SA@PLCC32 [DX2032]
AM27S291SA@SOIC24 [DX0133]
AM27S29A [DX0001]
AM27S29A@LCC20
AM27S29A@PLCC20 [DX2020]
AM27S29A@SOIC20 [DX1033]
AM27S29SA [DX0001]
AM27S29SA@PLCC20 [DX2020]
AM27S29SA@SOIC20 [DX1033]
AM27S31 [DX0001]
AM27S31@PLCC28 [DX2028]
AM27S31@PLCC32 [DX2032]
AM27S31@SOIC24 [DX0133]
AM27S31A [DX0001]
AM27S31A@PLCC28 [DX2028]
AM27S31A@PLCC32 [DX2032]
AM27S31A@SOIC24 [DX0133]
AM27S33 [DX0001]
AM27S33@PLCC20 [DX2020]
AM27S33@SOIC18 [DX1033]
AM27S33A [DX0001]
AM27S33A@PLCC20 [DX2020]
AM27S33A@SOIC18 [DX1033]
AM27S35 [DX0001]
AM27S35@PLCC28 [DX2028]
AM27S35@PLCC32 [DX2032]
AM27S35@SOIC24 [DX1033]
AM27S35A [DX0001]
AM27S35A@PLCC28 [DX2028]
AM27S35A@PLCC32 [DX2032]
AM27S35A@SOIC24 [DX1033]
AM27S37 [DX0001]
AM27S37@PLCC28 [DX2028]
AM27S37@PLCC32 [DX2032]
AM27S37@SOIC24 [DX1033]
AM27S37A [DX0001]
AM27S37A@PLCC28 [DX2028]
AM27S37A@PLCC32 [DX2032]
AM27S37A@SOIC24 [DX1033]
AM27S41 [DX0001]
AM27S41@PLCC28 [DX2028]
AM27S41@SOIC20 [DX1033]
AM27S41A [DX0001]
AM27S41A@PLCC28 [DX2028]
AM27S41A@SOIC20 [DX1033]
AM27S43 [DX0001]
AM27S43@PLCC28 [DX2028]
AM27S43@PLCC32 [DX2032]
AM27S43@SOIC24 [DX0133]
AM27S43A [DX0001]
AM27S43A@PLCC28 [DX2028]
AM27S43A@PLCC32 [DX2032]
AM27S43A@SOIC24 [DX0133]
AM27S45 [DX0001]
AM27S45@PLCC28 [DX2028]
AM27S45@PLCC32 [DX2032]
AM27S45@SOIC24 [DX1033]
AM27S45A [DX0001]

AM27S45A@PLCC28 [DX2028]
AM27S45A@PLCC32 [DX2032]
AM27S45A@SOIC24 [DX1033]
AM27S45SA [DX0001]
AM27S45SA@PLCC28 [DX2028]
AM27S45SA@PLCC32 [DX2032]
AM27S45SA@SOIC24 [DX1033]
AM27S47 [DX0001]
AM27S47@PLCC28 [DX2028]
AM27S47@PLCC32 [DX2032]
AM27S47@SOIC24 [DX1033]
AM27S47A [DX0001]
AM27S47A@PLCC28 [DX2028]
AM27S47A@PLCC32 [DX2032]
AM27S47A@SOIC24 [DX1033]
AM27S47SA [DX0001]
AM27S47SA@PLCC28 [DX2028]
AM27S47SA@PLCC32 [DX2032]
AM27S47SA@SOIC24 [DX1033]
AM27S49 [DX0001]
AM27S49@PLCC28 [DX2028]
AM27S49@PLCC32 [DX2032]
AM27S49@SOIC24 [DX0133]
AM27S49A [DX0001]
AM27S49A@PLCC28 [DX2028]
AM27S49A@PLCC32 [DX2032]
AM27S49A@SOIC24 [DX0133]
AM27S49SA [DX0001]
AM27S49SA@PLCC28 [DX2028]
AM27S49SA@PLCC32 [DX2032]
AM27S49SA@SOIC24 [DX0133]

PLD

AMPAL18P8 [DX0001]
AMPAL18P8@PLCC20 [DX2020]
AMPAL22V10 [DX0001]
AMPAL22V10@PLCC28 [DX2028]
AMPAL22V10A [DX0001]
AMPAL22V10A@PLCC28 [DX2028]
iM4A3-192/96@VQFP144 [DX3035]
iM4A5-192/96@VQFP144 [DX3035]
M4-128/64@PQFP100 [DX3022]
M4-128/64@TQFP100 [DX3021]
M4-128N/64@PLCC84 [DX2084]
M4-192/96@VQFP144 [DX3035]
M4-32/32@PLCC44 [DX2044]
M4-32/32@TQFP44 [DX3003]
M4-32/32@TQFP48 [DX3007]
M4-64/32@PLCC44 [DX2044]
M4-64/32@TQFP44 [DX3003]
M4-64/32@TQFP48 [DX3007]
M4-96/48@TQFP100 [DX3021]
M4A3-128/64@PQFP100 [DX3022]
M4A3-128/64@TQFP100 [DX3021]
M4A3-128N/64@PLCC84 [DX2084]
M4A3-32/32@PLCC44 [DX2044]
M4A3-32/32@TQFP44 [DX3003]
M4A3-32/32@TQFP48 [DX3007]
M4A3-384-160 [DX3118]
M4A3-384-192 [DX0001]
M4A3-512-160 [DX3118]
M4A3-512-192 [DX0001]
M4A3-512-256 [DX0001]
M4A3-64/32@PLCC44 [DX2044]
M4A3-64/32@TQFP44 [DX3003]
M4A3-64/32@TQFP48 [DX3007]
M4A3-64/64@TQFP100 [DX3021]
M4A3-96/48@TQFP100 [DX3021]
M4A5-128/64@PQFP100 [DX3022]
M4A5-128/64@TQFP100 [DX3021]
M4A5-128N/64@PLCC84 [DX2084]
M4A5-32/32@PLCC44 [DX2044]
M4A5-32/32@TQFP44 [DX3003]
M4A5-32/32@TQFP48 [DX3007]
M4A5-64/32@PLCC44 [DX2044]
M4A5-64/32@TQFP44 [DX3003]
M4A5-64/32@TQFP48 [DX3007]
M4A5-96/48@TQFP100 [DX3021]
M4LV-128/64@PQFP100 [DX3022]
M4LV-128/64@TQFP100 [DX3021]
M4LV-128N/64@PLCC84 [DX2084]
M4LV-32/32@PLCC44 [DX2044]
M4LV-32/32@TQFP44 [DX3003]
M4LV-32/32@TQFP48 [DX3007]
M4LV-64/32@PLCC44 [DX2044]
M4LV-64/32@TQFP44 [DX3003]
M4LV-64/32@TQFP48 [DX3007]
M4LV-96/48@TQFP100 [DX3021]
MACH110@PLCC44 [DX2044]

MACH111@PLCC44 [DX2044]
MACH111@TQFP44 [DX3003]
MACH120@PLCC68 [DX2068]
MACH130@PLCC84 [DX2084]
MACH131/1@PLCC84 [DX2084]
MACH131@PLCC84 [DX2084]
MACH131SP@PQFP100 [DX3022]
MACH131SP@TQFP100 [DX3021]
MACH210@PLCC44 [DX2044]
MACH210@TQFP44 [DX3003]
MACH210A@PLCC44 [DX2044]
MACH210A@TQFP44 [DX3003]
MACH210AQ@PLCC44 [DX2044]
MACH210AQ@TQFP44 [DX3003]
MACH211@PLCC44 [DX2044]
MACH211SP@PLCC44 [DX2044]
MACH211SP@TQFP44 [DX3003]
MACH215@PLCC44 [DX2044]
MACH220@PLCC68 [DX2068]
MACH221@PLCC68 [DX2068]
MACH231SP@PLCC84 [DX2084]
MACH231SP@PQFP100 [DX3022]
MACH231SP@TQFP100 [DX3021]
MACH435@PLCC84 [DX2084]
MACH436@PLCC84 [DX2084]
MACH446@PQFP100 [DX3022]
MACH446@TQFP100 [DX3021]
MACHLV210@PLCC44 [DX2044]
MACHLV210@TQFP44 [DX3003]
MACHLV436@PLCC84 [DX2084]
MACHLV446@PQFP100 [DX3022]
MACHLV446@TQFP100 [DX3021]
PAL10H8 [DX0001]
PAL10H8-2 [DX0001]
PAL10L8 [DX0001]
PAL10L8-2 [DX0001]
PAL12H6 [DX0001]
PAL12H6-2 [DX0001]
PAL12L6 [DX0001]
PAL12L6-2 [DX0001]
PAL14H4 [DX0001]
PAL14H4-2 [DX0001]
PAL14L4 [DX0001]
PAL14L4-2 [DX0001]
PAL16C1 [DX0001]
PAL16C1-2 [DX0001]
PAL16H2 [DX0001]
PAL16H2-2 [DX0001]
PAL16L2 [DX0001]
PAL16L2-2 [DX0001]
PAL16L8 [DX0001]
PAL16L8A [DX0001]
PAL16L8A@PLCC20 [DX2020]
PAL16L8A-2 [DX0001]
PAL16L8A-4 [DX0001]
PAL16L8B [DX0001]
PAL16L8B-2 [DX0001]
PAL16L8B-4 [DX0001]
PAL16L8D [DX0001]
PAL16L8H-10 [DX0001]
PAL16L8H-10@PLCC20 [DX0001]
PAL16L8H-10@SOIC20 [DX0001]
PAL16L8H-15 [DX0001]
PAL16R4 [DX0001]
PAL16R4A [DX0001]
PAL16R4A-2 [DX0001]
PAL16R4A-4 [DX0001]
PAL16R4B [DX0001]
PAL16R4B-2 [DX0001]
PAL16R4B-4 [DX0001]
PAL16R4D [DX0001]
PAL16R4H-10 [DX0001]
PAL16R4H-10@PLCC20 [DX0001]
PAL16R4H-10@SOIC20 [DX0001]
PAL16R4H-15 [DX0001]
PAL16R6 [DX0001]
PAL16R6A [DX0001]
PAL16R6A-2 [DX0001]
PAL16R6A-4 [DX0001]
PAL16R6B [DX0001]
PAL16R6B-2 [DX0001]
PAL16R6B-4 [DX0001]
PAL16R6D [DX0001]
PAL16R6H-15 [DX0001]
PAL16R8 [DX0001]
PAL16R8A [DX0001]
PAL16R8A-2 [DX0001]
PAL16R8A-4 [DX0001]
PAL16R8B [DX0001]
PAL16R8B-2 [DX0001]
PAL16R8B-4 [DX0001]
PAL16R8D [DX0001]
PAL16R8H-10 [DX0001]
PAL16R8H-10@PLCC20 [DX0001]
PAL16R8H-10@SOIC20 [DX0001]
PAL16R8H-15 [DX0001]

PAL16X4 [DX0001]
PAL20L8-10/2 [DX0001]
PAL20L8-10/2@PLCC28 [DX2028]
PAL20L8-10/2@SOIC24 [DX1033]
PAL20L8-5 [DX0001]
PAL20L8-5@PLCC28 [DX2028]
PAL20L8-5@SOIC24 [DX1033]
PAL20L8-7 [DX0001]
PAL20L8-7@PLCC28 [DX2028]
PAL20L8-7@SOIC24 [DX1033]
PAL20R4-10/2 [DX0001]
PAL20R4-10/2@PLCC28 [DX2028]
PAL20R4-10/2@SOIC24 [DX1033]
PAL20R4-5 [DX0001]
PAL20R4-5@PLCC28 [DX2028]
PAL20R4-5@SOIC24 [DX1033]
PAL20R4-7 [DX0001]
PAL20R4-7@PLCC28 [DX2028]
PAL20R4-7@SOIC24 [DX1033]
PAL20R6-10/2 [DX0001]
PAL20R6-10/2@PLCC28 [DX2028]
PAL20R6-10/2@SOIC24 [DX1033]
PAL20R6-5 [DX0001]
PAL20R6-5@PLCC28 [DX2028]
PAL20R6-5@SOIC24 [DX1033]
PAL20R6-7 [DX0001]
PAL20R6-7@PLCC28 [DX2028]
PAL20R6-7@SOIC24 [DX1033]
PAL20R8-10/2 [DX0001]
PAL20R8-10/2@PLCC28 [DX2028]
PAL20R8-10/2@SOIC24 [DX1033]
PAL20R8-5 [DX0001]
PAL20R8-5@PLCC28 [DX2028]
PAL20R8-5@SOIC24 [DX1033]
PAL20R8-7 [DX0001]
PAL20R8-7@PLCC28 [DX2028]
PAL20R8-7@SOIC24 [DX1033]
PAL22V10 [DX0001]
PAL22V10@PLCC28 [DX2028]
PAL22V10A [DX0001]
PAL22V10A@PLCC28 [DX2028]
PAL29M16H [DX0001]
PALC16L8Q [DX0001]
PALC16L8Q@PLCC20 [DX2020]
PALC16L8Z [DX0001]
PALC16L8Z@PLCC20 [DX2020]
PALC16R4Q [DX0001]
PALC16R4Q@PLCC20 [DX2020]
PALC16R4Z [DX0001]
PALC16R4Z@PLCC20 [DX2020]
PALC16R6Q [DX0001]
PALC16R6Q@PLCC20 [DX2020]
PALC16R6Z [DX0001]
PALC16R6Z@PLCC20 [DX2020]
PALC16R8Q [DX0001]
PALC16R8Q@PLCC20 [DX2020]
PALC16R8Z [DX0001]
PALC16R8Z@PLCC20 [DX2020]
PALCE16V8H [DX0001]
PALCE16V8H@PLCC20 [DX2020]
PALCE16V8H@SOIC20 [DX1033]
PALCE16V8Q [DX0001]
PALCE16V8Q@PLCC20 [DX2020]
PALCE16V8Q@SOIC20 [DX1033]
PALCE16V8Z [DX0001]
PALCE16V8Z@PLCC20 [DX2020]
PALCE16V8Z@SOIC20 [DX1033]
PALCE20RA10 [DX0001]
PALCE20RA10@PLCC28 [DX2028]
PALCE20RA10@SOIC24 [DX1033]
PALCE20RA10H [DX0001]
PALCE20RA10H@PLCC28 [DX2028]
PALCE20RA10H@SOIC24 [DX1033]
PALCE20RA10Q [DX0001]
PALCE20RA10Q@PLCC28 [DX2028]
PALCE20RA10Q@SOIC24 [DX1033]
PALCE20V8H [DX0001]
PALCE20V8H@PLCC28 [DX2028]
PALCE20V8H@SOIC24 [DX1003]
PALCE20V8Q [DX0001]
PALCE20V8Q@PLCC28 [DX2028]
PALCE20V8Q@SOIC24 [DX1003]
PALCE22V10H [DX0001]
PALCE22V10H@PLCC28 [DX2028]
PALCE22V10H@SOIC24 [DX1003]
PALCE22V10Q [DX0001]
PALCE22V10Q@PLCC28 [DX2028]
PALCE22V10Q@SOIC24 [DX1003]
PALCE22V10Z [DX0001]
PALCE22V10Z@PLCC28 [DX2028]
PALCE22V10Z@SOIC24 [DX1003]
PALCE26V12H/4 [DX0001]
PALCE26V12H/4@PLCC28 [DX2028]
PALCE26V12H/4@SOIC28 [DX1033]
PALCE26V12H-15 [DX0001]
PALCE26V12H-15@PLCC28 [DX2028]

PALCE26V12H-15@SOIC28 [DX1033]
PALCE26V12H-20 [DX0001]
PALCE26V12H-20@PLCC28 [DX2028]
PALCE26V12H-20@SOIC28 [DX1033]
PALCE26V12H-25 [DX0001]
PALCE26V12H-25@PLCC28 [DX2028]
PALCE26V12H-25@SOIC28 [DX1033]
PALCE29M16H [DX0001]
PALCE29M16H@PLCC28 [DX2028]
PALCE29M16H@SOIC24 [DX1033]
PALCE29MA16H [DX0001]
PALCE29MA16H@PLCC28 [DX2028]
PALCE29MA16H@SOIC24 [DX1033]
PALCE610 [DX0001]
PALCE610@PLCC28 [DX2028]
PALCE610@SOIC24 [DX1003]
PALCE610H [DX0001]
PALCE610H@PLCC28 [DX2028]
PALCE610H@SOIC24 [DX1003]
PALCE630H [DX0001]
PALCE630H@SOIC24 [DX1003]
PALCE630H-P28 [DX2028]
PALLV16V8 [DX0001]
PALLV16V8@PLCC20 [DX2020]
PALLV16V8@SOIC20 [DX1033]
PALLV16V8Z [DX0001]
PALLV16V8Z@PLCC20 [DX2020]
PALLV16V8Z@SOIC20 [DX1033]

MICROCONTROLLER

AM8751H [DX0001]
AM8753H [DX0001]
AM87C51 [DX0001]
AM87C51@PLCC44 [DX2044]
AM87C51@TQFP44 [DX3002]
AM87C521 [DX0001]
AM87C521@PLCC44 [DX2044]
AM87C521@TQFP44 [DX3002]
AM87C541 [DX0001]
AM87C541@PLCC44 [DX2044]
AM87C541@TQFP44 [DX3002]

AMIC

E(E)PROM/FRAM/NVRAM

A25L010 [DX0001]
A25L010[150mil]@SOP8 [DX1045#1]
A25L010[209mil]@SOP8 [DX1044#1]
A25L010A [DX0001]
A25L010A@SOP8 [DX1045#1]
A25L010A@TSSOP8 [DX1044#1]
A25L010A@USON8 [DX4002#1]
A25L010A@WSON8 [DX4005#1]
A25L016 [DX0001]
A25L016@SOP8 [DX1044#1]
A25L016T [DX4006#1]
A25L016T@SOP16 [DX1033#1]
A25L016T@SOP8(150mil) [DX1045#1]
A25L016T@SOP8(209mil) [DX1044#1]
A25L016T@WSON8 [DX4005#1]
A25L016U [DX4005#1]
A25L016U@SOP16 [DX1033#1]
A25L016U@SOP8(150mil) [DX1045#1]
A25L016U@SOP8(209mil) [DX1044#1]
A25L016U@WSON8 [DX4005#1]
A25L020 [DX0001]
A25L020[150mil]@SOP8 [DX1045#1]
A25L020[209mil]@SOP8 [DX1044#1]
A25L020B [DX0001]
A25L020B[150mil]@SOP8 [DX1045#1]
A25L020B[209mil]@SOP8 [DX1044#1]
A25L020C [DX0001]
A25L020C@SOP8 [DX1045#1]
A25L020C@USON8 [DX4002#1]
A25L020C@WSON8 [DX4005#1]
A25L032 [DX0001]
A25L032(NEW) [DX0001]
A25L032(NEW)@SOP16 [DX1072#1]
A25L032(NEW)@SOP8 [DX1044#1]
A25L032(OTP) [DX0001]
A25L032(OTP)@SOP16 [DX1033#1]

A25L032(OTP)@SOP8 [DX1044#1]
A25L032@SOP16 [DX1072#1]
A25L032@SOP8 [DX1044#1]
A25L032A [DX0001]
A25L032A@SOP16 [DX1072#1]
A25L032A@SOP8 [DX1044#1]
A25L040 [DX0001]
A25L040@QFN8 [DX4005#1]
A25L040@SOP16 [DX1033#1]
A25L040@SOP8 [DX1045#1]
A25L040A [DX0001]
A25L040A@SOP8(150 mil) [DX1045#1]
A25L040A@SOP8(209 mil) [DX1044#1]
A25L040A@WSON8 [DX4005#1]
A25L05P(Bottom) [DX0001]
A25L05P(Bottom)@QFN8 [DX4005#1]
A25L05P(Bottom)[150mil]@SOP8 [DX1045#1]
A25L05P(Bottom)[209mil]@SOP8 [DX1044#1]
A25L05P(Top) [DX0001]
A25L05P(Top)@QFN8 [DX4005#1]
A25L05P(Top)[150mil]@SOP8 [DX1045#1]
A25L05P(Top)[209mil]@SOP8 [DX1044#1]
A25L080 [DX0001]
A25L080@QFN8 [DX4005#1]
A25L080@SOP16
A25L080@SOP8 [DX1044#1]
A25L080A [DX0001]
A25L080A@QFN8 [DX4005#1]
A25L080A@SOP16
A25L080A@SOP8 [DX1044#1]
A25L080B [DX0001]
A25L080B@SOP8 [DX1044#1]
A25L080B@WSON8 [DX4005#1]
A25L10P(Bottom) [DX0001]
A25L10P(Bottom)@QFN8 [DX4005#1]
A25L10P(Bottom)[150mil]@SOP8 [DX1045#1]
A25L10P(Bottom)[209mil]@SOP8 [DX1044#1]
A25L10P(Top) [DX0001]
A25L10P(Top)@QFN8 [DX4005#1]
A25L10P(Top)[150mil]@SOP8 [DX1045#1]
A25L10P(Top)[209mil]@SOP8 [DX1044#1]
A25L16P(Bottom Boot)@QFN8 [DX4005#1]
A25L16P(Bottom Boot)@QFN8(ISP) [DX0001]
A25L16P(Bottom Boot)@SOP16 [DX1072#1]
A25L16P(Bottom Boot)@SOP16(ISP) [DX0001]
A25L16P(Bottom Boot)@SOP8 [DX1044#1]
A25L16P(Bottom Boot)@SOP8(ISP) [DX0001]
A25L16P(Top Boot)@QFN8 [DX4006#1]
A25L16P(Top Boot)@QFN8(ISP) [DX0001]
A25L16P(Top Boot)@SOP16 [DX1072#1]
A25L16P(Top Boot)@SOP16(ISP) [DX0001]
A25L16P(Top Boot)@SOP8 [DX1044#1]
A25L16P(Top Boot)@SOP8(ISP) [DX0001]
A25L20P(Bottom) [DX0001]
A25L20P(Bottom)@QFN8 [DX4005#1]
A25L20P(Bottom)[150mil]@SOP8 [DX1045#1]
A25L20P(Bottom)[209mil]@SOP8 [DX1044#1]
A25L20P(Top) [DX0001]
A25L20P(Top)@QFN8 [DX4005#1]
A25L20P(Top)[150mil]@SOP8 [DX1045#1]
A25L20P(Top)[209mil]@SOP8 [DX1044#1]
A25L40P(Bottom) [DX0001]
A25L40P(Bottom)@QFN8 [DX4005#1]
A25L40P(Bottom)@SOP16
A25L40P(Bottom)@SOP8 [DX1045#1]
A25L40P(Top) [DX0001]
A25L40P(Top)@QFN8 [DX4005#1]

A25L40P(Top)@SOP16
A25L40P(Top)@SOP8 [DX1045#1]
A25L42P(Bottom Boot) [DX0001]
A25L42P(Bottom Boot)@QFN8 [DX4005#1]
A25L42P(Bottom Boot)@SOP16 [DX1033#1]
A25L42P(Bottom Boot)@SOP8 [DX1045#1]
A25L42P(Top Boot) [DX0001]
A25L42P(Top Boot)@QFN8 [DX4005#1]
A25L42P(Top Boot)@SOP16 [DX1033#1]
A25L42P(Top Boot)@SOP8 [DX1045#1]
A25L512 [DX0001]
A25L512[150mil]@SOP8 [DX1045#1]
A25L512[209mil]@SOP8 [DX1044#1]
A25L5120 [DX0001]
A25L5120[150mil]@SOP8 [DX1045]
A25L5120[209mil]@SOP8 [DX1044]
A25L512A [DX0001]
A25L512A@SOP8 [DX1045#1]
A25L512A@TSSOP8 [DX1044#1]
A25L512A@USON8 [DX4002#1]
A25L512A@WSON8 [DX4005#1]
A25L80P [DX0001]
A25L80P@QFN8 [DX4005#1]
A25L80P@SOP16
A25L80P@SOP8 [DX1044#1]
A25L82P(Bottom Boot) [DX0001]
A25L82P(Bottom Boot)@QFN8 [DX4005#1]
A25L82P(Bottom Boot)@SOP16 [DX1033#1]
A25L82P(Bottom Boot)@SOP8 [DX1044#1]
A25L82P(Top Boot) [DX0001]
A25L82P(Top Boot)@QFN8 [DX4005#1]
A25L82P(Top Boot)@SOP16 [DX1033#1]
A25L82P(Top Boot)@SOP8 [DX1044#1]
A25LQ032A [DX0001]
A25LQ032A@SOP16 [DX1072#1]
A25LQ032A@SOP8 [DX1044#1]
A25LQ16 [DX0001]
A25LQ16@SOP8 [DX1044#1]
A25LQ16@WSON8 [DX4005#1]
A25LQ32B [DX0001]
A25LQ32B@SOP8 [DX1044#1]
A25LQ32B@WSON8 [DX4005#1]
A25LQ64@BGA24 [DX5146]
A25LQ64@SOP16 [DX1072#1]
A25LQ64@SOP8 [DX1044#1]
A25LQ64@WSON8 [DX4005#1]
A25LQ64N@BGA24 [DX5146]
A25LQ64N@SOP16 [DX1072#1]
A25LQ64N@SOP8 [DX1044#1]
A25LQ64N@WSON8 [DX4005#1]
A25LS080 [DX0001]
A25LS080@QFN8 [DX4005#1]
A25LS080@SOP16 [DX1033#1]
A25LS080@SOP8 [DX1044#1]
A25LS512 [DX0001]
A25LS512[150mil]@SOP8 [DX1045#1]
A25LS512[209mil]@SOP8 [DX1044#1]
A25LS5120 [DX0001]
A25LS5120[150mil]@SOP8 [DX1045#1]
A25LS5120[209mil]@SOP8 [DX1044#1]
A27020 [DX0001]
A27020@PLCC32 [DX2032]
A27020@TSOP32 [DX1002]
A27020L [DX0001]
A27020L@PLCC32 [DX2032]
A27020L@TSOP32 [DX1002]
A275308 [DX0001]
A275308@PLCC32 [DX2032]
A276308 [DX0001]
A276308(E) [DX0001]
A276308(E)@PLCC32 [DX2032]
A276308(E)@SOIC28 [DX1033]
A276308@PLCC32 [DX2032]
A276308@SOIC28 [DX1033]
A276308A [DX0001]
A276308A(L) [DX0001]
A276308A(L)@PLCC32 [DX2032]
A276308A(L)@SOIC28 [DX1033]

A276308A@PLCC32 [DX2032]
A276308A@SOIC28 [DX1033]
A277308 [DX0001]
A277308@PLCC32 [DX2032]
A277308A [DX0001]
A277308A@PLCC32 [DX2032]
A278308 [DX0001]
A278308@PLCC32 [DX2032]
A278308A [DX0001]
A278308A(L) [DX0001]
A278308A(L)@PLCC32 [DX2032]
A278308A@PLCC32 [DX2032]
A279308 [DX0001]
A279308@PLCC32 [DX2032]
A290011T [DX0001]
A290011T@PLCC32 [DX2032]
A290011T@TSOP32 [DX1002]
A290011U [DX0001]
A290011U@PLCC32 [DX2032]
A290011U@TSOP32 [DX1002]
A29001T [DX0001]
A29001T@PLCC32 [DX2032]
A29001T@TSOP32 [DX1002]
A29001U [DX0001]
A29001U@PLCC32 [DX2032]
A29001U@TSOP32 [DX1002]
A290021T [DX0001]
A290021T@PLCC32 [DX2032]
A290021T@TSOP32 [DX1002]
A290021U [DX0001]
A290021U@PLCC32 [DX2032]
A290021U@TSOP32 [DX1002]
A29002T [DX0001]
A29002T@PLCC32 [DX2032]
A29002T@TSOP32 [DX1002]
A29002U [DX0001]
A29002U@PLCC32 [DX2032]
A29002U@TSOP32 [DX1002]
A29010 [DX0001]
A29010@PLCC32 [DX2032]
A29010@TSOP32 [DX1002]
A29040 [DX0001]
A29040@PLCC32 [DX2032]
A29040@TSOP32 [DX1002]
A29040A [DX0001]
A29040A@PLCC32 [DX2032]
A29040A@TSOP32 [DX1002]
A29040B [DX0001]
A29040B@PLCC32 [DX2032]
A29040B@TSOP32 [DX1002]
A29040C [DX0001]
A29040C@PLCC32 [DX2032]
A29040C@TSOP32 [DX1002]
A29160ATG@FBGA48 [DX5002]
A29160ATV@TSOP48 [DX1004]
A29160AUG@FBGA48 [DX5002]
A29160AUV@TSOP48 [DX1004]
A29160TG@FBGA48 [DX5002]
A29160TM@PSOP44 [DX1014]
A29160TV@TSOP48 [DX1004]
A29160UG@FBGA48 [DX5002]
A29160UM@PSOP44 [DX1014]
A29160UV@TSOP48 [DX1004]
A29400TM@PSOP44 [DX1014]
A29400TV@TSOP48 [DX1004]
A29400UM@PSOP44 [DX1014]
A29400UV@TSOP48 [DX1004]
A29512 [DX0001]
A29512@PLCC32 [DX2032]
A29512@TSOP32 [DX1002]
A29512A [DX0001]
A29512A@PLCC32 [DX2032]
A29512A@TSOP32 [DX1002]
A29800ATG@FBGA48 [DX5002]
A29800ATV@TSOP48 [DX1004]
A29800AUG@FBGA48 [DX5002]
A29800AUV@TSOP48 [DX1004]
A29800TM@PSOP44 [DX1014]
A29800TV@TSOP48 [DX1004]
A29800UM@PSOP44 [DX1014]
A29800UV@TSOP48 [DX1004]
A29801ATG@FBGA48 [DX5002]
A29801ATV@TSOP48 [DX1004]
A29801AUG@FBGA48 [DX5002]
A29801AUV@TSOP48 [DX1004]
A29801TM@PSOP44 [DX1014]
A29801TV@TSOP48 [DX1004]
A29801UM@PSOP44 [DX1014]
A29801UV@TSOP48 [DX1004]
A29DL162TG@FBGA48 [DX5002]
A29DL162TV@TSOP48 [DX1004]
A29DL162UG@FBGA48 [DX5002]
A29DL162UV@TSOP48 [DX1004]
A29DL163TG@FBGA48 [DX5002]
A29DL163TV@TSOP48 [DX1004]
A29DL163UG@FBGA48 [DX5002]

A29DL163UV@TSOP48 [DX1004]
A29DL164TV@TSOP48 [DX1004]
A29DL164UV@TSOP48 [DX1004]
A29DL320FUV@TSOP48 [DX1004]
A29DL322TV@TSOP48 [DX1004]
A29DL322UV@TSOP48 [DX1004]
A29DL323TV(old)@FBGA63 [DX5047]
A29DL323TV@TSOP48 [DX1004]
A29DL323UV(old)@FBGA63 [DX5047]
A29DL323UV@TSOP48 [DX1004]
A29DL324TV(old)@FBGA63 [DX5047]
A29DL324TV@TSOP48 [DX1004]
A29DL324UV(old)@FBGA63 [DX5047]
A29DL324UV@TSOP48 [DX1004]
A29L004ATV@TSOP32 [DX1002]
A29L004ATY@VSOP32 [DX1003]
A29L004AUV@TSOP32 [DX1002]
A29L004AUY@VSOP32 [DX1003]
A29L004T@TSOP32 [DX1002]
A29L004T@VSOP32 [DX1003]
A29L004U@TSOP32 [DX1002]
A29L004U@VSOP32 [DX1003]
A29L008AUV@TSOP40 [DX1006]
A29L008U@TSOP40 [DX1006]
A29L040@PLCC32 [DX2032]
A29L040@VSOP32 [DX1003]
A29L160ATM@PSOP44 [DX1014]
A29L160AUG@FBGA48 [DX5002]
A29L160AUV@TSOP48 [DX1004]
A29L160BTG@FBGA48 [DX5002]
A29L160BUG@FBGA48 [DX5002]
A29L160FTV@TSOP48 [DX1004]
A29L160HTG@FBGA48 [DX5002]
A29L160HUG@FBGA48 [DX5002]
A29L160TG@FBGA48 [DX5002]
A29L160TV@TSOP48 [DX1004]
A29L160UM@PSOP44 [DX1014]
A29L320ATG@FBGA48 [DX5002]
A29L320AUG@FBGA48 [DX5002]
A29L400ATG@FBGA48 [DX5002]
A29L400ATV@TSOP48 [DX1004]
A29L400AUM@PSOP44 [DX1014]
A29L400TG@FBGA48 [DX5002]
A29L400TV@TSOP48 [DX1004]
A29L400UM@PSOP44 [DX1014]
A29L800ATG@FBGA48 [DX5002]
A29L800ATV@TSOP48 [DX1004]
A29L800AUM@PSOP44 [DX1014]
A29DL164TG@FBGA48 [DX5002]
A29DL164UG@FBGA48 [DX5002]
A29DL320FTV@TSOP48 [DX1004]
A29DL322TG@FBGA48 [DX5002]
A29DL322UG@FBGA48 [DX5002]
A29DL323TG@FBGA48 [DX5002]
A29DL323TV(old)@TSOP48 [DX1004]
A29DL323UG@FBGA48 [DX5002]
A29DL323UV(old)@TSOP48 [DX1004]
A29DL324TG@FBGA48 [DX5002]
A29DL324TV(old)@TSOP48 [DX1004]
A29DL324UG@FBGA48 [DX5002]
A29DL324UV(old)@TSOP48 [DX1004]
A29L004ATL@PLCC32 [DX2032]
A29L004ATW@TSOP40 [DX1006]
A29L004AUL@PLCC32 [DX2032]
A29L004AUW@TSOP40 [DX1006]
A29L004T@PLCC32 [DX2032]
A29L004T@TSOP40 [DX1006]
A29L004U@PLCC32 [DX2032]
A29L004U@TSOP40 [DX1006]
A29L008ATV@TSOP40 [DX1006]
A29L008T@TSOP40 [DX1006]
A29L040 [DX0001]
A29L040@TSOP32 [DX1002]
A29L160ATG@FBGA48 [DX5002]
A29L160ATV@TSOP48 [DX1004]
A29L160AUM@PSOP44 [DX1014]
A29L160AUV@TSOP48(slow) [DX1004]
A29L160BTV@TSOP48 [DX1004]
A29L160BUV@TSOP48 [DX1004]
A29L160FUV@TSOP48 [DX1004]
A29L160HTV@TSOP48 [DX1004]
A29L160HUV@TSOP48 [DX1004]
A29L160TM@PSOP44 [DX1014]
A29L160UG@FBGA48 [DX5002]
A29L160UV@TSOP48 [DX1004]
A29L320ATV@TSOP48 [DX1004]
A29L320AUV@TSOP48 [DX1004]
A29L400ATM@PSOP44 [DX1014]
A29L400AUG@FBGA48 [DX5002]
A29L400AUV@TSOP48 [DX1004]
A29L400TM@PSOP44 [DX1014]
A29L400UG@FBGA48 [DX5002]
A29L400UV@TSOP48 [DX1004]
A29L800ATM@PSOP44 [DX1014]
A29L800AUG@FBGA48 [DX5002]
A29L800AUV@TSOP48 [DX1004]

A29L800HTG@FBGA48 [DX5002]
A29L800HTM@PSOP44 [DX1014]
A29L800HTV@TSOP48 [DX1004]
A29L800HUG@FBGA48 [DX5002]
A29L800HUM@PSOP44 [DX1014]
A29L800HUV@TSOP48 [DX1004]
A29L800TG@FBGA48 [DX5002]
A29L800TM@PSOP44 [DX1014]
A29L800TV@TSOP48 [DX1004]
A29L800UG@FBGA48 [DX5002]
A29L800UM@PSOP44 [DX1014]
A29L800UV@TSOP48 [DX1004]
A49LF004@PLCC32 [DX2032]
A49LF004@VSOP32 [DX1003]
A49LF004M@PLCC32 [DX2032]
A49LF004M@VSOP32 [DX1003]
A49LF040AT@PLCC32 [DX2032]
A49LF040AT@VSOP32 [DX1003]
A49LF040T@PLCC32 [DX2032]
A49LF040T@VSOP32 [DX1003]
A50FW040@PLCC32 [DX2032]
A50FW040@VSOP32 [DX1003]
A50FW040M@PLCC32 [DX2032]
A50FW040M@VSOP32 [DX1003]
A50LPW040@PLCC32 [DX2032]
A50LPW040@VSOP32 [DX1003]
A617308 [DX0001]
A617308@TSOP32 [DX0001]
A61L5308 [DX0001]
A61L5308@TSOP28 [DX1024]
A623308(M) [DX0001]
A623308(R)@TSOP28 [DX1024]
A623308(V)@TSOP28 [DX1024]
A625308(M) [DX0001]
A625308(R)@TSOP28 [DX1024]
A625308(V)@TSOP28 [DX1024]
A62L256 [DX0001]
A62L256(M) [DX0001]
A62L256(R)@TSOP28 [DX1024]
A62L256(V)@TSOP28 [DX1024]
A62S6308(M) [DX0001]
A62S6308(U)@BGA48 [DX0001]
A62S6308(X)@TSOP32 [DX0001]
A62S7308A(M) [DX0001]
A62S7308A(U)@BGA48 [DX0001]
A62S7308A(X)@TSOP32 [DX0001]
A62S8308A(M) [DX0001]
A62S8308A(U)@BGA48 [DX0001]
A62S8308A(X)@TSOP32 [DX0001]
A62W5308(M) [DX0001]
A62W5308(R)@TSOP28 [DX1024]
A62W5308(V)@TSOP28 [DX1024]
A81L801TG@FBGA69 [DX5001]
A81L801UG@FBGA69 [DX5001]
A82DL1622TG@FBGA69 [DX5001]
A82DL1622UG@FBGA69 [DX5001]
A82DL1624TG@FBGA69 [DX5001]
A82DL1624UG@FBGA69 [DX5001]
A82DL1632TG@FBGA69 [DX5001]
A82DL1632UG@FBGA69 [DX5001]
A82DL1634TG@FBGA69 [DX5001]
A82DL1634UG@FBGA69 [DX5001]
A82DL1642TG@FBGA69 [DX5001]
A82DL1642UG@FBGA69 [DX5001]
A82DL1644TG@FBGA69 [DX5001]
A82DL1644UG@FBGA69 [DX5001]
A82DL32216TG@FBGA69 [DX5001]
A82DL32216UG@FBGA69 [DX5001]
A82DL3224TG@FBGA69 [DX5001]
A82DL3224UG@FBGA69 [DX5001]
A82DL3228TG@FBGA69 [DX5001]
A82DL3228UG@FBGA69 [DX5001]
A82DL32316TG@FBGA69 [DX5001]
A82DL32316UG@FBGA69 [DX5001]
A82DL3234TG@FBGA69 [DX5001]
A82DL3234UG@FBGA69 [DX5001]
A82DL3238TG@FBGA69 [DX5001]
A82DL3238UG@FBGA69 [DX5001]
A82DL32416TG@FBGA69 [DX5001]
A82DL32416UG@FBGA69 [DX5001]
A82DL3244TG@FBGA69 [DX5001]
A82DL3244UG@FBGA69 [DX5001]
A82DL3248TG@FBGA69 [DX5001]
A82DL3248UG@FBGA69 [DX5001]

AMS

MICROCONTROLLER

AS5030 [DX1001]
AS5031 [DX1001]
AS5032 [DX1001]
AS5033 [DX1001]
AS5034 [DX1001]
AS5035 [DX1001]

ANACHIP

E(E)PROM/FRAM/NVRAM

27CX010 [DX0001]
27CX010@PLCC32 [DX2032]
27CX010@TSOP32 [DX1002]
27CX256 [DX0001]
27CX321 [DX0001]
27CX322 [DX0001]
27CX641 [DX0001]
27CX642 [DX0001]
93C46 [DX0001]
93C46@SOIC8 [DX1045]
93C46A [DX0001]
93C46A@SOIC8 [DX1045]
93C56A [DX0001]
93C56A@SOIC8 [DX1045]
93C66A [DX0001]
93C66A@SOIC8 [DX1045]
93CX46 [DX0001]
93CX46@SOIC8 [DX1045]
93CX56 [DX0001]
93CX56@SOIC8 [DX1045]
93CX66 [DX0001]
93CX66@SOIC8 [DX1045]
AM24LC02 [DX0001]
AM24LC02@SOIC8 [DX1045]
AM24LC02@TSSOP8 [DX1059]
AM24LC04 [DX0001]
AM24LC04@SOIC8 [DX1045]
AM24LC04@TSSOP8 [DX1059]
AM24LC08 [DX0001]
AM24LC08@SOIC8 [DX1045]
AM24LC08@TSSOP8 [DX1059]
AM24LC16 [DX0001]
AM24LC16@SOIC8 [DX1045]
AM24LC16@TSSOP8 [DX1059]
AM24LC21 [DX0001]
AM24LC21@SOIC8 [DX1045]
AM24LC21@TSSOP8 [DX1059]
AM24LC21B [DX0001]
AM24LC21B@SOIC8 [DX1045]
AM24LC21B@TSSOP8 [DX1059]
AM93LC46(08bit) [DX0001]
AM93LC46(08bit)@SOIC8 [DX1045]
AM93LC46(08bit)@TSOP8 [DX1059]
AM93LC46(16bit) [DX0001]
AM93LC46(16bit)@SOIC8 [DX1045]
AM93LC46(16bit)@TSOP8 [DX1059]
AM93LC56(08bit) [DX0001]
AM93LC56(08bit)@SOIC8 [DX1045]
AM93LC56(08bit)@TSOP8 [DX1059]
AM93LC56(16bit) [DX0001]
AM93LC56(16bit)@SOIC8 [DX1045]
AM93LC56(16bit)@TSOP8 [DX1059]
AM93LC66(08bit) [DX0001]
AM93LC66(08bit)@SOIC8 [DX1045]
AM93LC66(08bit)@TSOP8 [DX1059]
AM93LC66(16bit) [DX0001]
AM93LC66(16bit)@SOIC8 [DX1045]
AM93LC66(16bit)@TSOP8 [DX1059]
AM93LC86(08bit) [DX0001]
AM93LC86(08bit)@SOIC8 [DX1045]
AM93LC86(08bit)@TSOP8 [DX1059]
AM93LC86(16bit) [DX0001]
AM93LC86(16bit)@SOIC8 [DX1045]
AM93LC86(16bit)@TSOP8 [DX1059]

PLD

PA7024 [DX0001]
PA7024(J)@PLCC28 [DX2028]
PA7024(JN)@PLCC28 [DX2028]
PA7024@SOIC24 [DX1033]
PA7140 [DX0001]
PA7140@PLCC44 [DX2044]

PA7140@TQFP44 [DX3003]
PA7540 [DX0001]
PA7540(J)@PLCC28 [DX2028]
PA7540(JN)@PLCC28 [DX2028]
PA7572 [DX0001]
PA7572@PLCC44 [DX2044]
PA7572@TQFP44 [DX3003]
PEEL18CV8J@PLCC20 [DX2020]
PEEL18CV8P [DX0001]
PEEL18CV8S@SOIC20 [DX1033]
PEEL18CV8T@TSOP20 [DX1000]
PEEL18CV8Z [DX0001]
PEEL18CV8Z@PLCC20 [DX2020]
PEEL18CV8Z@SOIC20 [DX1033]
PEEL18CV8Z@TSOP20 [DX1000]
PEEL18LV8Z [DX0001]
PEEL18LV8Z@PLCC20 [DX2020]
PEEL18LV8Z@SOIC20 [DX1033]
PEEL18LV8Z@TSOP20 [DX1000]
PEEL22CV10A [DX0001]
PEEL22CV10A@PLCC28 [DX2028]
PEEL22CV10A@SOIC24 [DX1033]
PEEL22CV10A@TSOP24 [DX1000]
PEEL22CV10A+ [DX0001]
PEEL22CV10A+@PLCC28 [DX2028]
PEEL22CV10A+@SOIC24 [DX1033]
PEEL22CV10A+@TSOP24 [DX1000]
PEEL22CV10A++ [DX0001]
PEEL22CV10A++@PLCC28 [DX2028]
PEEL22CV10A++@SOIC24 [DX1033]
PEEL22CV10A++@TSOP24 [DX1000]
PEEL22CV10AZ [DX0001]
PEEL22CV10AZ@PLCC28 [DX2028]
PEEL22CV10AZ@SOIC24 [DX1033]
PEEL22CV10AZ@TSOP24 [DX1000]
PEEL22CV10AZ+ [DX0001]
PEEL22CV10AZ+@PLCC28 [DX2028]
PEEL22CV10AZ+@SOIC24 [DX1033]
PEEL22CV10AZ+@TSOP24 [DX1000]
PEEL22CV10AZ++ [DX0001]
PEEL22CV10AZ++@PLCC28 [DX2028]
PEEL22CV10AZ++@SOIC24 [DX1033]
PEEL22CV10AZ++@TSOP24 [DX1000]
PEEL22LV10AZ [DX0001]
PEEL22LV10AZ@PLCC28 [DX2028]
PEEL22LV10AZ@SOIC24 [DX1033]
PEEL22LV10AZ@TSOP24 [DX1000]
PEEL22LV10AZ+ [DX0001]
PEEL22LV10AZ+@PLCC28 [DX2028]
PEEL22LV10AZ+@SOIC24 [DX1033]
PEEL22LV10AZ+@TSOP24 [DX1000]
PEEL22LV10AZ++ [DX0001]
PEEL22LV10AZ++@PLCC28 [DX2028]
PEEL22LV10AZ++@SOIC24 [DX1033]
PEEL22LV10AZ++@TSOP24 [DX1000]

APLUS FLASH

E(E)PROM/FRAM/NVRAM

AF24BC01 [DX0001]
AF24BC01@SOIC8 [DX1045]
AF24BC01@TSSOP8 [DX1059]
AF24BC02 [DX0001]
AF24BC02@SOIC8 [DX1045]
AF24BC02@TSSOP8 [DX1059]
AF24BC04 [DX0001]
AF24BC04@SOIC8 [DX1045]
AF24BC04@TSSOP8 [DX1059]
AF24BC08 [DX0001]
AF24BC08@SOIC8 [DX1045]
AF24BC08@TSSOP8 [DX1059]
AF24BC128 [DX0001]
AF24BC128@SOIC8 [DX1045]
AF24BC128@TSOP8 [DX1059]
AF24BC16 [DX0001]
AF24BC16@SOIC8 [DX1045]
AF24BC16@TSSOP8 [DX1059]
AF24BC256 [DX0001]
AF24BC256@SOIC8 [DX1045]
AF24BC256@TSOP8 [DX1059]
AF24BC32 [DX0001]
AF24BC32@SOIC8 [DX1045]
AF24BC32@TSOP8 [DX1059]
AF24BC64 [DX0001]
AF24BC64@SOIC8 [DX1045]
AF24BC64@TSOP8 [DX1059]
AF24C128 [DX0001]

AF24C128@SOIC8 [DX1045]
AF24C128@TSOP8 [DX1059]
AF24C256 [DX0001]
AF24C256@SOIC8 [DX1045]
AF24C256@TSOP8 [DX1059]
AF24C32 [DX0001]
AF24C32@SOIC8 [DX1045]
AF24C32@TSOP8 [DX1059]
AF24C64 [DX0001]
AF24C64@SOIC8 [DX1045]
AF24C64@TSOP8 [DX1059]
AF25BC08 [DX0001]
AF25BC08@SOIC8 [DX1045]
AF25BC08@TSOP8 [DX1059]
AF25BC128 [DX0001]
AF25BC128@SOIC8 [DX1045#1]
AF25BC128@TSOP8 [DX1059#1]
AF25BC16 [DX0001]
AF25BC16@SOIC8 [DX1045]
AF25BC16@TSOP8 [DX1059]
AF25BC256 [DX0001]
AF25BC256@SOIC8 [DX1045#1]
AF25BC256@TSOP8 [DX1059#1]
AF25BC32 [DX0001]
AF25BC32@SOIC8 [DX1045]
AF25BC32@TSOP8 [DX1059]
AF25BC64 [DX0001]
AF25BC64@SOIC8 [DX1045]
AF25BC64@TSOP8 [DX1059]
AF93BC46(08bit) [DX0001]
AF93BC46(08bit)@SOIC8 [DX1045]
AF93BC46(08bit)@TSOP8 [DX1059]
AF93BC46(16bit) [DX0001]
AF93BC46(16bit)@SOIC8 [DX1045]
AF93BC46(16bit)@TSOP8 [DX1059]
AF93BC56(08bit) [DX0001]
AF93BC56(08bit)@SOIC8 [DX1045]
AF93BC56(08bit)@TSOP8 [DX1059]
AF93BC56(16bit) [DX0001]
AF93BC56(16bit)@SOIC8 [DX1045]
AF93BC56(16bit)@TSOP8 [DX1059]
AF93BC66(08bit) [DX0001]
AF93BC66(08bit)@SOIC8 [DX1045]
AF93BC66(08bit)@TSOP8 [DX1059]
AF93BC66(16bit) [DX0001]
AF93BC66(16bit)@SOIC8 [DX1045]
AF93BC66(16bit)@TSOP8 [DX1059]
AF93BC86(08bit) [DX0001]
AF93BC86(08bit)@SOIC8 [DX1045]
AF93BC86(08bit)@TSOP8 [DX1059]
AF93BC86(16bit) [DX0001]
AF93BC86(16bit)@SOIC8 [DX1045]
AF93BC86(16bit)@TSOP8 [DX1059]
AF93C46(08bit) [DX0001]
AF93C46(08bit)@SOIC8 [DX1045]
AF93C46(08bit)@TSOP8 [DX1059]
AF93C46(16bit) [DX0001]
AF93C46(16bit)@SOIC8 [DX1045]
AF93C46(16bit)@TSOP8 [DX1059]
AF93C56(08bit) [DX0001]
AF93C56(08bit)@SOIC8 [DX1045]
AF93C56(08bit)@TSOP8 [DX1059]
AF93C56(16bit) [DX0001]
AF93C56(16bit)@SOIC8 [DX1045]
AF93C56(16bit)@TSOP8 [DX1059]
AF93C66(08bit) [DX0001]
AF93C66(08bit)@SOIC8 [DX1045]
AF93C66(08bit)@TSOP8 [DX1059]
AF93C66(16bit) [DX0001]
AF93C66(16bit)@SOIC8 [DX1045]
AF93C66(16bit)@TSOP8 [DX1059]
AF93C86(08bit) [DX0001]
AF93C86(08bit)@SOIC8 [DX1045]
AF93C86(08bit)@TSOP8 [DX1059]
AF93C86(16bit) [DX0001]
AF93C86(16bit)@SOIC8 [DX1045]
AF93C86(16bit)@TSOP8 [DX1059]

ARTSCHIP

E(E)PROM/FRAM/NVRAM

24AA02 [DX0001]
24AA02@DFN8 [DX4002]
24AA02@MSOP8 [DX1015]
24AA02@SOIC8 [DX1045]
24AA02@SOT5 [DX1041]
24AA02@TSSOP8 [DX1059]

24LC01A [DX0001]
24LC01A@dBGA8
24LC01A@MAP8
24LC01A@SOIC8 [DX1045]
24LC01A@SOT5 [DX1041]
24LC01A@TSSOP8 [DX1059]
24LC01B [DX0001]
24LC01B@SOIC8 [DX1045]
24LC01B@SOT5 [DX1041]
24LC01B@TSSOP8 [DX1059]
24LC02A [DX0001]
24LC02A@dBGA8
24LC02A@MAP8
24LC02A@SOIC8 [DX1045]
24LC02A@SOT5 [DX1041]
24LC02A@TSSOP8 [DX1059]
24LC02B [DX0001]
24LC02B@DFN8 [DX4002]
24LC02B@MSOP8 [DX1015]
24LC02B@SOIC8 [DX1045]
24LC02B@SOT5 [DX1041]
24LC02B@TSSOP8 [DX1059]
24LC04A [DX0001]
24LC04A@dBGA8
24LC04A@MAP8
24LC04A@SOIC8 [DX1045]
24LC04A@SOT5 [DX1041]
24LC04A@TSSOP8 [DX1059]
24LC04B [DX0001]
24LC04B@DFN8 [DX4002]
24LC04B@MSOP8 [DX1015]
24LC04B@SOIC8 [DX1045]
24LC04B@SOT5 [DX1041]
24LC04B@TSSOP8 [DX1059]
24LC08A [DX0001]
24LC08A@dBGA8
24LC08A@MAP8
24LC08A@SOIC8 [DX1045]
24LC08A@SOT5 [DX1041]
24LC08A@TSSOP8 [DX1059]
24LC08B [DX0001]
24LC08B@DFN8 [DX4002]
24LC08B@MSOP8 [DX1015]
24LC08B@SOIC8 [DX1045]
24LC08B@SOT5 [DX1041]
24LC08B@TSSOP8 [DX1059]
24LC16A [DX0001]
24LC16A@dBGA8
24LC16A@MAP8
24LC16A@SOIC8 [DX1045]
24LC16A@SOT5 [DX1041]
24LC16A@TSSOP8 [DX1059]
24LC256B [DX0001]
24LC256B@MSOP8 [DX1015]
24LC256B@SOIC8 [DX1045]
24LC256B@TSSOP8 [DX1059]
24LC32 [DX0001]
24LC32@SOIC14 [DX1000]
24LC32@SOIC8 [DX1045]
24LC32@TSSOP8 [DX1059]
24LC64 [DX0001]
24LC64@SOIC14 [DX1000]
24LC64@SOIC8 [DX1045]
24LC64@TSSOP8 [DX1059]

ASAHI KASEI(AKM)

E(E)PROM/FRAM/NVRAM

AK27CX321 [DX0001]
AK27CX322 [DX0001]
AK27CX641 [DX0001]
AK27CX642 [DX0001]
AK6002A(F)@SOP8 [DX1045]
AK6002A(V)@TSSOP8 [DX1059]
AK6003A(V)@TSSOP8 [DX1059]
AK6004A(F)@SOP8 [DX1045]
AK6004A(M)@SSOP8 [DX1044]
AK6008A(F)@SOP8 [DX1045]
AK6010A(F)@SOP8 [DX1045]
AK6012A(F)@SOP8 [DX1045]
AK6416A(M)@SSOP8 [DX1000]
AK6416C(F)@SOP8 [DX1045]
AK6420A(F)@SOP8 [DX1045]
AK6420A(M)@SSOP8 [DX1000]
AK6420B(H)@MSOP8 [DX1015]
AK6440A(F)@SOP8 [DX1045]
AK6440A(M)@SSOP8 [DX1000]
AK6440B(H)@MSOP8 [DX1015]

AK6480A(F)@SOP8 [DX1045]
AK6480A(M)@SSOP8 [DX1000]
AK6480B(H)@MSOP8 [DX1015]
AK6480C(F)@SOP8 [DX1045]
AK6480C(H)@MSOP8 [DX1015]
AK6480C(L)@SON8 [DX0001]
AK6480C(M)@SSOP8 [DX1000]
AK6481C(H)@MSOP8 [DX1015]
AK6481C(M)@SSOP8 [DX1000]
AK6508C(T)@MSOP8 [DX1015]
AK6508C(U)@USON8 [DX0001]
AK6510C(L)@SONW8 [DX0001]
AK6510C(M)@SSOP8 [DX1059]
AK6512C(L)@SONW8 [DX0001]
AK6512C(M)@SSOP8 [DX1059]
AK6514C(F)@SOP8 [DX1016]
AK6514C(N)@QFN20 [DX4011]
AK6516C(F)@SOP8 [DX1016]
AK93C10A(F)@SOP8 [DX1045]
AK93C41A(V)@TSSOP8 [DX1059]
AK93C45 [DX0001]
AK93C45(F)@SOP8 [DX1045]
AK93C45A(F)@SOP8 [DX1045]
AK93C45A(NF)@SOP8 [DX1045]
AK93C45A(V)@TSSOP8 [DX1059]
AK93C45B(H)@MSOP8 [DX1015]
AK93C45B(L)@SON8 [DX5156]
AK93C45C(T)@MSOP8 [DX1015]
AK93C45C(U)@USON8 [DX5156]
AK93C45L [DX0001]
AK93C45L(F)@SOP8 [DX1045]
AK93C46 [DX0001]
AK93C46(F)@SOP8 [DX1045]
AK93C46A(F)@SOP8 [DX1045]
AK93C46A(NF)@SOP8 [DX1045]
AK93C46A(V)@TSSOP8 [DX1059]
AK93C46B(H)@MSOP8 [DX1015]
AK93C46B(L)@SON8 [DX5156]
AK93C46C(T)@MSOP8 [DX1015]
AK93C46C(U)@USON8 [DX5156]
AK93C46L [DX0001]
AK93C46L(F)@SOP8 [DX1045]
AK93C51A(V)@TSSOP8 [DX1059]
AK93C55 [DX0001]
AK93C55(F)@SOP8 [DX1045]
AK93C55A(F)@SOP8 [DX1045]
AK93C55A(NF)@SOP8 [DX1045]
AK93C55A(V)@TSSOP8 [DX1059]
AK93C55B(H)@MSOP8 [DX1015]
AK93C55B(L)@SON8 [DX5156]
AK93C55C(T)@MSOP8 [DX1015]
AK93C55C(U)@USON8 [DX5156]
AK93C55L [DX0001]
AK93C55L(F)@SOP8 [DX1045]
AK93C56 [DX0001]
AK93C56(F)@SOP8 [DX1045]
AK93C56A(F)@SOP8 [DX1045]
AK93C56A(NF)@SOP8 [DX1045]
AK93C56A(V)@TSSOP8 [DX1059]
AK93C56B(H)@MSOP8 [DX1015]
AK93C56B(L)@SON8 [DX5156]
AK93C56C(T)@MSOP8 [DX1015]
AK93C56C(U)@USON8 [DX5156]
AK93C56L [DX0001]
AK93C56L(F)@SOP8 [DX1045]
AK93C61A(V)@TSSOP8 [DX1059]
AK93C65 [DX0001]
AK93C65(F)@SOP8 [DX1045]
AK93C65A(F)@SOP8 [DX1045]
AK93C65A(NF)@SOP8 [DX1045]
AK93C65A(V)@TSSOP8 [DX1059]
AK93C65B(H)@MSOP8 [DX1015]
AK93C65B(L)@SON8 [DX5156]
AK93C65C(T)@MSOP8 [DX1015]
AK93C65C(U)@USON8 [DX5156]
AK93C65L [DX0001]
AK93C65L(F)@SOP8 [DX1045]
AK93C66 [DX0001]
AK93C66(F)@SOP8 [DX1045]
AK93C66A(F)@SOP8 [DX1045]
AK93C66A(NF)@SOP8 [DX1045]
AK93C66A(V)@TSSOP8 [DX1059]
AK93C66B(H)@MSOP8 [DX1015]
AK93C66B(L)@SON8 [DX5156]
AK93C66C(T)@MSOP8 [DX1015]
AK93C66C(U)@USON8 [DX5156]
AK93C66L [DX0001]
AK93C66L(F)@SOP8 [DX1045]
AK93C75 [DX0001]
AK93C75(F)@SOP8 [DX1045]
AK93C75A(F)@SOP8 [DX1045]
AK93C75A(NF)@SOP8 [DX1045]
AK93C75A(V)@TSSOP8 [DX1059]
AK93C75B(H)@MSOP8 [DX1015]
AK93C75L [DX0001]
AK93C75L(F)@SOP8 [DX1045]

AK93C85 [DX0001]
AK93C85L [DX0001]
AK93C95A(F)@SOP8 [DX1045]
AK9824(M)@SSOP8 [DX1000]
AK93C85(F)@SOP8 [DX1045]
AK93C85L(F)@SOP8 [DX1045]
AK9822(M)@SSOP8 [DX1000]
AK9844@SOIC14 [DX1016]

ASD

E(E)PROM/FRAM/NVRAM

AE29F1008 [DX0001]
AE29F2008 [DX0001]

ASI

E(E)PROM/FRAM/NVRAM

AS58C1001 [DX0001]
AS58C1001@SSOP32 [DX1020]
AS58C1001@PLCC32 [DX2032]

Asic Microelectronics

E(E)PROM/FRAM/NVRAM

AX24C02@SOP8 [DX1045]
AX24C08@SOP8 [DX1045]
AX24C04@SOP8 [DX1045]
AX24C16@SOP8 [DX1045]

ASP

MICROCONTROLLER

AP827C51 [DX0001]
AP827C52 [DX0001]
AP827C54 [DX0001]
AP827C58 [DX0001]
AP827C51@PLCC44 [DX2044]
AP827C52@PLCC44 [DX2044]
AP827C54@PLCC44 [DX2044]
AP827C58@PLCC44 [DX2044]

ASTIGP-MICROCHIP

MICROCONTROLLER

PIC16F616 [DX0001]
PIC16F616@SOIC14 [DX1016]
PIC16F616@QFN16 [DX4010]
PIC16F616@TSSOP14 [DX1000]

ATC

E(E)PROM/FRAM/NVRAM

ATC24C02 [DX0001]
ATC24C02@SOIC8 [DX1045]
ATC24C02@TSSOP8 [DX1059]
ATC24C04 [DX0001]
ATC24C04@SOIC8 [DX1045]
ATC24C04@TSSOP8 [DX1059]
ATC24C08 [DX0001]
ATC24C08@SOIC8 [DX1045]
ATC24C08@TSSOP8 [DX1059]
ATC24C16 [DX0001]
ATC24C16@SOIC8 [DX1045]
ATC24C16@TSSOP8 [DX1059]
ATC24LC02 [DX0001]
ATC24LC02@SOIC8 [DX1045]
ATC24LC02@TSSOP8 [DX1059]
ATC24LC02A [DX0001]
ATC24LC02A@SOIC8 [DX1045]
ATC24LC02A@TSSOP8 [DX1059]
ATC24LC04 [DX0001]
ATC24LC04@SOIC8 [DX1045]
ATC24LC04@TSSOP8 [DX1059]
ATC24LC08 [DX0001]
ATC24LC08@SOIC8 [DX1045]
ATC24LC08@TSSOP8 [DX1059]
ATC24LC16 [DX0001]
ATC24LC16@SOIC8 [DX1045]
ATC24LC16@TSSOP8 [DX1059]
ATC93C46(08bit) [DX0001]
ATC93C46(08bit)@SOIC8 [DX1045]
ATC93C46(16bit) [DX0001]
ATC93C46(16bit)@SOIC8 [DX1045]
ATC93C46R(08bit)@SOIC8 [DX1045]
ATC93C46R(16bit)@SOIC8 [DX1045]
ATC93C56(08bit) [DX0001]
ATC93C56(08bit)@SOIC8 [DX1045]
ATC93C56(16bit) [DX0001]
ATC93C56(16bit)@SOIC8 [DX1045]
ATC93C56R(08bit)@SOIC8 [DX1045]
ATC93C56R(16bit)@SOIC8 [DX1045]
ATC93C66(08bit) [DX0001]
ATC93C66(08bit)@SOIC8 [DX1045]
ATC93C66(16bit) [DX0001]
ATC93C66(16bit)@SOIC8 [DX1045]
ATC93C66R(08bit)@SOIC8 [DX1045]
ATC93C66R(16bit)@SOIC8 [DX1045]
ATC93LC46(08bit) [DX0001]
ATC93LC46(08bit)@SOIC8 [DX1045]
ATC93LC46(16bit) [DX0001]
ATC93LC46(16bit)@SOIC8 [DX1045]
ATC93LC46R(08bit)@SOIC8 [DX1045]
ATC93LC46R(16bit)@SOIC8 [DX1045]
ATC93LC56(08bit) [DX0001]
ATC93LC56(08bit)@SOIC8 [DX1045]
ATC93LC56(16bit) [DX0001]
ATC93LC56(16bit)@SOIC8 [DX1045]
ATC93LC56R(08bit)@SOIC8 [DX1045]
ATC93LC56R(16bit)@SOIC8 [DX1045]
ATC93LC66(08bit) [DX0001]
ATC93LC66(08bit)@SOIC8 [DX1045]
ATC93LC66(16bit) [DX0001]
ATC93LC66(16bit)@SOIC8 [DX1045]
ATC93LC66R(08bit)@SOIC8 [DX1045]
ATC93LC66R(16bit)@SOIC8 [DX1045]

ATMEL

E(E)PROM/FRAM/NVRAM

AT17C002@PLCC20 [DX2020]
AT17C002@PLCC44 [DX2044]
AT17C002@SOIC20 [DX1033]
AT17C002@TQFP44 [DX3005]
AT17C002A@PLCC20 [DX2020]
AT17C002A@TQFP32 [DX3001]
AT17C010 [DX0001]
AT17C010@PLCC20 [DX2020]
AT17C010A [DX0001]
AT17C010A@PLCC20 [DX2020]
AT17C020@PLCC20 [DX2020]
AT17C020A@PLCC20 [DX2020]
AT17C040@PLCC44 [DX2044]
AT17C040@TQFP44 [DX3005]
AT17C128 [DX0001]
AT17C128@PLCC20 [DX2020]

AT17C128@SOIC20 [DX1033]
AT17C128@SOIC8 [DX1045]
AT17C128A@PLCC20 [DX2020]
AT17C256 [DX0001]
AT17C256@PLCC20 [DX2020]
AT17C256@SOIC20 [DX1033]
AT17C256@SOIC8 [DX1045]
AT17C256A@PLCC20 [DX2020]
AT17C512 [DX0001]
AT17C512@PLCC20 [DX2020]
AT17C512A [DX0001]
AT17C512A@PLCC20 [DX2020]
AT17C65 [DX0001]
AT17C65@PLCC20 [DX2020]
AT17C65@SOIC20 [DX1033]
AT17C65@SOIC8 [DX1045]
AT17C65A@PLCC20 [DX2020]
AT17F040@LAP8 [DX4024]
AT17F040@PLCC20 [DX2020]
AT17F040@PLCC20(Virtex Pinout) [DX2020]
AT17F040A@LAP8 [DX4024]
AT17F040A@PLCC20 [DX2020]
AT17F040A@TQFP32 [DX3001]
AT17F080@LAP8 [DX4024]
AT17F080@PLCC20 [DX2020]
AT17F080@PLCC44 [DX2044]
AT17F080@TQFP44 [DX3005]
AT17F080A@LAP8 [DX4024]
AT17F080A@PLCC20 [DX2020]
AT17F080A@TQFP32 [DX3001]
AT17F16@LAP8 [DX4024]
AT17F16@PLCC20 [DX2020]
AT17F16@PLCC44 [DX2044]
AT17F16@TQFP44 [DX3005]
AT17F16A@LAP8 [DX4024]
AT17F16A@PLCC20 [DX2020]
AT17F32@PLCC44 [DX2044]
AT17F32A@PLCC44 [DX2044]
AT17LV002@PLCC20 [DX2020]
AT17LV002@PLCC44 [DX2044]
AT17LV002@SOIC20 [DX1033]
AT17LV002@TQFP44 [DX3005]
AT17LV002A@PLCC20 [DX2020]
AT17LV002A@TQFP32 [DX3001]
AT17LV010 [DX0001]
AT17LV010@PLCC20 [DX2020]
AT17LV010A [DX0001]
AT17LV010A@PLCC20 [DX2020]
AT17LV020@PLCC20 [DX2020]
AT17LV020A@PLCC20 [DX2020]
AT17LV040@PLCC44 [DX2044]
AT17LV040@TQFP44 [DX3005]
AT17LV128 [DX0001]
AT17LV128@PLCC20 [DX2020]
AT17LV128@SOIC20 [DX1033]
AT17LV128@SOIC8 [DX1045]
AT17LV128A@PLCC20 [DX2020]
AT17LV256 [DX0001]
AT17LV256@PLCC20 [DX2020]
AT17LV256@SOIC20 [DX1033]
AT17LV256@SOIC8 [DX1045]
AT17LV256A@PLCC20 [DX2020]
AT17LV512 [DX0001]
AT17LV512@PLCC20 [DX2020]
AT17LV512A [DX0001]
AT17LV512A@PLCC20 [DX2020]
AT17LV65 [DX0001]
AT17LV65@PLCC20 [DX2020]
AT17LV65@SOIC20 [DX1033]
AT17LV65@SOIC8 [DX1045]
AT17LV65A@PLCC20 [DX2020]
AT17N002@SOIC20 [DX1033]
AT17N002@TQFP44 [DX3005]
AT17N010 [DX0001]
AT17N010@SOIC20 [DX1033]
AT17N040@TQFP44 [DX3005]
AT17N256 [DX0001]
AT17N256@SOIC20 [DX1033]
AT17N256@SOIC8 [DX1045]
AT17N512 [DX0001]
AT17N512@SOIC20 [DX1033]
AT24C01 [DX0001]
AT24C01@MSOP8 [DX1015]
AT24C01@SOIC8 [DX1045]
AT24C01@TSSOP8 [DX1059]
AT24C01A [DX0001]
AT24C01A@MAP8 [DX4047]
AT24C01A@SOIC8 [DX1045]
AT24C01A@SOT23-5 [DX1041]
AT24C01A@TSSOP8 [DX1059]
AT24C01B [DX0001]
AT24C01B@dBGA2 [DX5156]
AT24C01B@MAP8 [DX4047]
AT24C01B@SOIC8 [DX1045]

AT24C01B@SOT23 [DX1041]
AT24C01B@TSSOP8 [DX1059]
AT24C01C [DX0001]
AT24C01C@dBGA8 [DX5156]
AT24C01C@MAP8 [DX4047]
AT24C01C@SOIC8 [DX1045]
AT24C01C@SOT23 [DX1041]
AT24C01C@TSSOP8 [DX1059]
AT24C01D [DX0001]
AT24C01D@dBGA8 [DX5156]
AT24C01D@MAP8 [DX4047]
AT24C01D@SOIC8 [DX1045]
AT24C01D@SOT23 [DX1041]
AT24C01D@TSSOP8 [DX1059]
AT24C02 [DX0001]
AT24C02@SOIC8 [DX1016]
AT24C02@TSSOP8 [DX1059]
AT24C02A [DX0001]
AT24C02A@SOIC8 [DX1045]
AT24C02A@TSSOP8 [DX1059]
AT24C02B [DX0001]
AT24C02B(HAIER) [DX0001]
AT24C02B@dBGA2 [DX5156]
AT24C02B@MAP8 [DX4047]
AT24C02B@SOIC8 [DX1045]
AT24C02B@SOT23 [DX1041]
AT24C02B@TSSOP8 [DX1059]
AT24C02C [DX0001]
AT24C02C@dBGA8 [DX5156]
AT24C02C@SOIC8 [DX1045]
AT24C02C@SOT23 [DX1041]
AT24C02C@TSSOP8 [DX1059]
AT24C02C@UDFN8 [DX4047]
AT24C02D [DX0001]
AT24C02D@dBGA8 [DX5156]
AT24C02D@SOIC8 [DX1045]
AT24C02D@SOT23 [DX1041]
AT24C02D@TSSOP8 [DX1059]
AT24C02D@UDFN8 [DX4047]
AT24C04 [DX0001]
AT24C04@MAP8 [DX4047]
AT24C04@SOIC8 [DX1045]
AT24C04@SOT23-5 [DX1041]
AT24C04@TSSOP8 [DX1059]
AT24C04A [DX0001]
AT24C04A@MAP8 [DX4047]
AT24C04A@SOIC8 [DX1045]
AT24C04A@TSSOP8 [DX1059]
AT24C04B [DX0001]
AT24C04B@dBGA2 [DX5156]
AT24C04B@MAP8 [DX4047]
AT24C04B@SOIC8 [DX1045]
AT24C04B@SOT23 [DX1041]
AT24C04B@TSSOP8 [DX1059]
AT24C04C [DX0001]
AT24C04C@dBGA8 [DX5156]
AT24C04C@SOIC8 [DX1045]
AT24C04C@SOT23 [DX1041]
AT24C04C@TSSOP8 [DX1059]
AT24C04C@UDFN8 [DX4047]
AT24C04D [DX0001]
AT24C04D@dBGA8 [DX5156]
AT24C04D@SOIC8 [DX1045]
AT24C04D@SOT23 [DX1041]
AT24C04D@TSSOP8 [DX1059]
AT24C04D@UDFN8 [DX4047]
AT24C08 [DX0001]
AT24C08@MAP8 [DX4047]
AT24C08@SOIC8 [DX1045]
AT24C08@TSSOP8 [DX1059]
AT24C08A [DX0001]
AT24C08A@MAP8 [DX4047]
AT24C08A@SOIC8 [DX1045]
AT24C08A@TSSOP8 [DX1059]
AT24C08B [DX0001]
AT24C08B@dBGA2 [DX5156]
AT24C08B@MAP8 [DX4047]
AT24C08B@SOIC8 [DX1045]
AT24C08B@SOT23 [DX1041]
AT24C08B@TSSOP8 [DX1059]
AT24C08C [DX0001]
AT24C08C@dBGA8 [DX5156]
AT24C08C@SOIC8 [DX1045]
AT24C08C@SOT23 [DX1041]
AT24C08C@TSSOP8 [DX1059]
AT24C08C@UDFN8 [DX4047]
AT24C08D [DX0001]
AT24C08D@dBGA8 [DX5156]
AT24C08D@SOIC8 [DX1045]
AT24C08D@SOT23 [DX1041]
AT24C08D@TSSOP8 [DX1059]
AT24C08D@UDFN8 [DX4047]
AT24C1024 [DX0001]
AT24C1024@LAP8 [DX4006]
AT24C1024@SAP8 [DX4005]
AT24C1024@SOIC8 [DX1044]

AT24C1024B(1.8V) [DX0001]
AT24C1024B(1.8V)@LAP8 [DX4006]
AT24C1024B(1.8V)@SAP8 [DX4005]
AT24C1024B(1.8V)@SOIC8(150mil) [DX1045]
AT24C1024B(1.8V)@SOIC8(200mil) [DX1044]
AT24C1024B(1.8V)@TSSOP8 [DX1059]
AT24C1024B(2.5V) [DX0001]
AT24C1024B(2.5V)@LAP8 [DX4006]
AT24C1024B(2.5V)@SAP8 [DX4005]
AT24C1024B(2.5V)@SOIC8(150mil) [DX1045]
AT24C1024B(2.5V)@SOIC8(200mil) [DX1044]
AT24C1024B(2.5V)@TSSOP8 [DX1059]
AT24C11 [DX0001]
AT24C11@SOIC8 [DX1045]
AT24C11@TSSOP8 [DX1059]
AT24C128(1.8V) [DX0001]
AT24C128(1.8V)@MAP8 [DX4047]
AT24C128(1.8V)@SAP8 [DX4005]
AT24C128(1.8V)@SOIC8 [DX1045]
AT24C128(1.8V)@TSSOP8 [DX1059]
AT24C128(2.7V) [DX0001]
AT24C128(2.7V)@MAP8 [DX4047]
AT24C128(2.7V)@SAP8 [DX4005]
AT24C128(2.7V)@SOIC8 [DX1045]
AT24C128(2.7V)@SSOP8 [DX1044]
AT24C128(2.7V)@TSSOP8 [DX1059]
AT24C128B [DX0001]
AT24C128B@MAP8 [DX4047]
AT24C128B@SAP8 [DX4005]
AT24C128B@SOIC8 [DX1045]
AT24C128B@TSSOP8 [DX1059]
AT24C128C@SOIC8 [DX1045]
AT24C128C@TSSOP8 [DX1059]
AT24C128C@UDFN8 [DX4047]
AT24C128C@VFBGA8 [DX5156]
AT24C128C@XDFN8 [DX0001]
AT24C16 [DX0001]
AT24C16@SOIC8 [DX1045]
AT24C16@TSSOP8 [DX1059]
AT24C164 [DX0001]
AT24C164@SOIC8 [DX1045]
AT24C16A [DX0001]
AT24C16A@MAP8 [DX4047]
AT24C16A@SOIC8 [DX1045]
AT24C16A@TSSOP8 [DX1059]
AT24C16B [DX0001]
AT24C16B@MAP8 [DX4047]
AT24C16B@SOIC8 [DX1045]
AT24C16B@TSSOP8 [DX1059]
AT24C16C [DX0001]
AT24C16C@dBGA8 [DX5156]
AT24C16C@SOIC8 [DX1045]
AT24C16C@SOT23 [DX1041]
AT24C16C@TSSOP8 [DX1059]
AT24C16C@UDFN8 [DX4047]
AT24C16C@XDFN8 [DX0001]
AT24C21 [DX4047]
AT24C21@SOIC8 [DX1045]
AT24C256(1.8V) [DX0001]
AT24C256(1.8V)@MAP8 [DX4047]
AT24C256(1.8V)@SAP8 [DX4005]
AT24C256(1.8V)@SOIC8 [DX1045]
AT24C256(1.8V)@TSSOP8 [DX1059]
AT24C256(2.7V) [DX0001]
AT24C256(2.7V)@MAP8 [DX4047]
AT24C256(2.7V)@SAP8 [DX4005]
AT24C256(2.7V)@SOIC8 [DX1045]
AT24C256(2.7V)@TSSOP8 [DX1059]
AT24C256B [DX0001]
AT24C256B@MAP8 [DX4047]
AT24C256B@SAP8 [DX4005]
AT24C256B@SOIC8 [DX1045]
AT24C256B@TSSOP8 [DX1059]
AT24C256C [DX0001]
AT24C256C@dBGA8 [DX5156]
AT24C256C@SOIC8 [DX1045]
AT24C256C@TSSOP8 [DX1059]
AT24C256C@UDFN8 [DX4047]
AT24C32 [DX0001]
AT24C32@SOIC8 [DX1045]
AT24C32@TSSOP8 [DX1059]
AT24C32A [DX0001]
AT24C32A@MAP8 [DX4047]
AT24C32A@SOIC8 [DX1045]
AT24C32A@TSSOP8 [DX1059]
AT24C32C [DX0001]
AT24C32C@dBGA8 [DX5156]
AT24C32C@MAP8 [DX4047]
AT24C32C@SAP8 [DX4005]
AT24C32C@SOIC8 [DX1045]
AT24C32C@TSSOP8 [DX1059]

AT24C32D@SOIC8 [DX1045]
AT24C32D@SOT23 [DX4047]
AT24C32D@TSSOP8 [DX1059]
AT24C32D@UDFN8 [DX4047]
AT24C32D@VDFN8 [DX0001]
AT24C32D@XBGA8 [DX0001]
AT24C512(1.8V) [DX0001]
AT24C512(1.8V)@LAP8 [DX4006]
AT24C512(1.8V)@SAP8 [DX4005]
AT24C512(1.8V)@SOIC8 [DX1045]
AT24C512(1.8V)@TSSOP8 [DX1059]
AT24C512(2.7V) [DX0001]
AT24C512(2.7V)@LAP8 [DX4006]
AT24C512(2.7V)@SAP8 [DX4005]
AT24C512(2.7V)@SOIC8 [DX1045]
AT24C512(2.7V)@TSSOP8 [DX1059]
AT24C512B [DX0001]
AT24C512B@LAP8 [DX4006]
AT24C512B@SAP8 [DX4005]
AT24C512B@SOIC8(150 mil) [DX1045]
AT24C512B@SOIC8(200 mil) [DX1044]
AT24C512B@TSSOP8 [DX1059]
AT24C512C@SOIC8(150 mil) [DX1045]
AT24C512C@SOIC8(200 mil) [DX1044]
AT24C512C@TSSOP8 [DX1059]
AT24C512C@UDFN8 [DX4002]
AT24C512C@VFBGA8 [DX5156]
AT24C64 [DX0001]
AT24C64@SOIC8 [DX1045]
AT24C64@TSSOP8 [DX1059]
AT24C64A [DX0001]
AT24C64A@MAP8 [DX4047]
AT24C64A@SOIC8 [DX1045]
AT24C64A@TSSOP8 [DX1059]
AT24C64B [DX0001]
AT24C64B@SOIC8 [DX1045]
AT24C64B@TSSOP8 [DX1059]
AT24C64C [DX0001]
AT24C64C@dBGA8 [DX5156]
AT24C64C@MAP8 [DX4047]
AT24C64C@SAP8 [DX4005]
AT24C64C@SOIC8 [DX1045]
AT24C64C@TSSOP8 [DX1059]
AT24C64D@SOIC8 [DX1045]
AT24C64D@SOT23 [DX4047]
AT24C64D@TSSOP8 [DX1059]
AT24C64D@UDFN8 [DX4047]
AT24C64D@VDFN8 [DX0001]
AT24C64D@XBGA8 [DX0001]
AT24CM01@SOIC8[150 mil] [DX1045]
AT24CM01@SOIC8[200 mil] [DX1044]
AT24CM01@TSSOP8 [DX1059]
AT24CM01@WLCSP8 [DX0001]
AT24CM02@SOIC8[150 mil] [DX1045]
AT24CM02@SOIC8[200 mil] [DX1044]
AT24CM02@TSSOP8 [DX1059]
AT24CM02@WLCSP8 [DX0001]
AT24CS01@SOIC8 [DX1045]
AT24CS01@SOT23 [DX1041]
AT24CS01@TSSOP8 [DX1059]
AT24CS01@UDFN8 [DX4047]
AT24CS02@SOIC8 [DX1045]
AT24CS02@SOT23 [DX1041]
AT24CS02@TSSOP8 [DX1059]
AT24CS02@UDFN8 [DX4047]
AT24CS04@SOIC8 [DX1045]
AT24CS04@SOT23 [DX1041]
AT24CS04@TSSOP8 [DX1059]
AT24CS04@UDFN8 [DX4047]
AT24CS08@SOIC8 [DX1045]
AT24CS08@SOT23 [DX1041]
AT24CS08@TSSOP8 [DX1059]
AT24CS08@UDFN8 [DX4047]
AT24CS128 [DX0001]
AT24CS128@SOIC8 [DX1045]
AT24CS16 [DX0001]
AT24CS16@MAP8 [DX4047]
AT24CS16@SOIC8 [DX1045]
AT24CS16@TSSOP8 [DX1059]
AT24HC02B [DX0001]
AT24HC02B@SOIC8 [DX1045]
AT24HC02B@TSSOP8 [DX1059]
AT24HC02C [DX0001]
AT24HC02C@SOIC8 [DX1045]
AT24HC04B [DX0001]
AT24HC04B@MAP8 [DX4047]
AT24HC04B@SOIC8 [DX1045]
AT24HC04B@TSSOP8 [DX1059]
AT24HC0CB@TSSOP8 [DX1059]
AT24MAC402@SOIC8 [DX1045]

AT24MAC402@SOT23 [DX1041]
AT24MAC402@UDFN8 [DX4047]
AT24MAC602@SOT23 [DX1041]
AT24MAC602@UDFN8 [DX4047]
AT24RF08AT@TSSOP14 [DX1000]
AT24RF08BT@TSSOP14 [DX1000]
AT24RF08CT@TSSOP14 [DX1000]
AT25010@SOIC8 [DX1045]
AT25010A@SOIC8 [DX1045]
AT25010B [DX0001]
AT25010B@TSSOP8 [DX1059]
AT25020@SOIC8 [DX1045]
AT25020A@SOIC8 [DX1045]
AT25020B [DX0001]
AT25020B@TSSOP8 [DX1059]
AT25040(ISP) [DX0001]
AT25040@SOIC8(ISP)
AT25040A(ISP) [DX0001]
AT25040A@SOIC8(ISP)
AT25080@SOIC8 [DX1045]
AT25080@TSSOP20 [DX1000]
AT25080A [DX0001]
AT25080A@TSSOP14 [DX1000]
AT25080B [DX0001]
AT25080B@MAP8 [DX4002]
AT25080B@TSSOP8 [DX1059]
AT25128@SOIC16 [DX1016]
AT25128@TSSOP14 [DX1000]
AT25128A [DX0001]
AT25128A@SAP8 [DX4005]
AT25128A@SOIC8(5.4) [DX1044]
AT25128A@TSSOP8 [DX1059]
AT25128B@SOIC8 [DX1045]
AT25128B@UDFN8 [DX4002]
AT25160 [DX0001]
AT25160@TSSOP14 [DX1000]
AT25160@TSSOP8 [DX1059]
AT25160A@SOIC8 [DX1045]
AT25160A@TSSOP8 [DX1059]
AT25160B@dBGA8
AT25160B@SOIC8 [DX1045]
AT25256 [DX0001]
AT25256@SOIC8 [DX1045]
AT25256@TSSOP20 [DX1001]
AT25256A@dBGA8
AT25256A@SOIC8(4.0) [DX1045]
AT25256A@TSSOP14 [DX1000]
AT25256B [DX0001]
AT24MAC402@TSSOP8 [DX1059]
AT24MAC602@SOIC8 [DX1045]
AT24MAC602@TSSOP8 [DX1059]
AT24RF08AN@SOIC8 [DX1045]
AT24RF08BN@SOIC8 [DX1045]
AT24RF08CN@SOIC8 [DX1045]
AT25010 [DX0001]
AT25010A [DX0001]
AT25010A@TSSOP8 [DX1059]
AT25010B@SOIC8 [DX1045]
AT25020 [DX0001]
AT25020A [DX0001]
AT25020A@TSSOP8 [DX1059]
AT25020B@SOIC8 [DX1045]
AT25040 [DX0001]
AT25040@SOIC8 [DX1045]
AT25040A [DX0001]
AT25040A@SOIC8 [DX1045]
AT25080 [DX0001]
AT25080@TSSOP14 [DX1000]
AT25080@TSSOP8 [DX1059]
AT25080A@SOIC8 [DX1045]
AT25080A@TSSOP8 [DX1059]
AT25080B@dBGA8
AT25080B@SOIC8 [DX1045]
AT25128 [DX0001]
AT25128@SOIC8 [DX1045]
AT25128@TSSOP20 [DX1000]
AT25128A@dBGA8
AT25128A@SOIC8(4.0) [DX1045]
AT25128A@TSSOP14 [DX1000]
AT25128B [DX0001]
AT25128B@TSSOP8 [DX1059]
AT25128B@VFBGA8 [DX0001]
AT25160@SOIC8 [DX1045]
AT25160@TSSOP20 [DX1000]
AT25160A [DX0001]
AT25160A@TSSOP14 [DX1000]
AT25160B [DX0001]
AT25160B@MAP8 [DX4002]
AT25160B@TSSOP8 [DX1059]
AT25256@SOIC16 [DX1016]
AT25256@TSSOP14 [DX1000]
AT25256A [DX0001]
AT25256A@SAP8 [DX4005]
AT25256A@SOIC8(5.4) [DX1044]
AT25256A@TSSOP8 [DX1059]
AT25256B@SOIC8 [DX1045]

AT25256B@TSSOP8 [DX1059]
AT25256B@UDFN8 [DX4002]
AT25256B@VFBGA8 [DX0001]
AT25320 [DX0001]
AT25320@SOIC8 [DX1045]
AT25320@TSSOP14 [DX1000]
AT25320@TSSOP20 [DX1000]
AT25320@TSSOP8 [DX1059]
AT25320A [DX0001]
AT25320A@SOIC8 [DX1045]
AT25320A@TSSOP14 [DX1000]
AT25320A@TSSOP8 [DX1059]
AT25320B [DX0001]
AT25320B@dBGA8
AT25320B@MAP8 [DX4002]
AT25320B@SOIC8 [DX1045]
AT25320B@TSSOP8 [DX1059]
AT25512@SAP8 [DX4005]
AT25512@SOIC8 [DX1045]
AT25512@TSSOP8 [DX1059]
AT25640 [DX0001]
AT25640@SOIC8 [DX1045]
AT25640@TSSOP14 [DX1000]
AT25640@TSSOP20 [DX1000]
AT25640@TSSOP8 [DX1059]
AT25640A [DX0001]
AT25640A@SOIC8 [DX1045]
AT25640A@TSSOP14 [DX1000]
AT25640A@TSSOP8 [DX1059]
AT25640B [DX0001]
AT25640B@dBGA8
AT25640B@MAP8 [DX4002]
AT25640B@SOIC8 [DX1045]
AT25640B@TSSOP8 [DX1059]
AT25DF021(OTP)@SOIC8 [DX1045#2]
AT25DF021(OTP)@UDFN8 [DX4005#3]
AT25DF021@SOIC8 [DX1045#2]
AT25DF021@UDFN8 [DX4005#3]
AT25DF041A@MLF8 [DX4005#3]
AT25DF041A@SOIC8(4.0) [DX1045#2]
AT25DF041A@SOIC8(5.4) [DX1044#2]
AT25DF081@SOIC8 [DX1045#2]
AT25DF081@UDFN8 [DX4005#3]
AT25DF081A@SOIC8 [DX1044#1]
AT25DF081A@UDFN8 [DX4005#3]
AT25DF161(OTP)@SOIC8(4.0) [DX1045#2]
AT25DF161(OTP)@SOIC8(5.4) [DX1031#2]
AT25DF161(OTP)@UDFN8 [DX4005#3]
AT25DF161@MLF8 [DX4005#3]
AT25DF161@SOIC8(4.0) [DX1045#2]
AT25DF161@SOIC8(5.4) [DX1031#2]
AT25DF321@SOIC16 [DX1033#2]
AT25DF321@SOIC8 [DX1031#2]
AT25DF321A(OTP)@SOIC16 [DX1033#2]
AT25DF321A(OTP)@SOIC8 [DX1031#2]
AT25DF321A(OTP)@UDFN8 [DX4005#3]
AT25DF641(OTP)@SOIC16 [DX1033#2]
AT25DF641(OTP)@VDFN8 [DX4006#2]
AT25DL161@dBGA8 [DX5156]
AT25DL161@SOIC8 [DX1045#2]
AT25DL161@UDFN8 [DX4005#3]
AT25DN011@DFN8 [DX4002#1]
AT25DN011@SOIC8 [DX1045#2]
AT25DN011@TSSOP8 [DX1059#3]
AT25DQ321@SOIC16 [DX1033#2]
AT25DQ321@SOIC8 [DX1031#2]
AT25DQ321@UDFN8 [DX4005#3]
AT25F1024 [DX0001]
AT25F1024(W)@SOIC8 [DX1044]
AT25F1024(W)@VQFPN8 [DX4006]
AT25F1024@SOIC8 [DX1045]
AT25F1024@VQFPN8 [DX4005]
AT25F1024A [DX0001]
AT25F1024A(W)@SOIC8 [DX1044]
AT25F1024A(W)@VQFPN8 [DX4006]
AT25F1024A@SOIC8 [DX1045]
AT25F1024A@VQFPN8 [DX4005]
AT25F2048 [DX0001]
AT25F2048(W)@SOIC8 [DX1044]
AT25F2048(W)@VQFPN8 [DX4006]
AT25F2048@SOIC8 [DX1045]
AT25F2048@VQFPN8 [DX4005]
AT25F2048A [DX0001]
AT25F2048A(W)@SOIC8 [DX1044]
AT25F2048A(W)@VQFPN8 [DX4006]
AT25F2048A@SOIC8 [DX1045]
AT25F2048A@VQFPN8 [DX4005]
AT25F4096 [DX0001]
AT25F4096(W)@SOIC8 [DX1044]
AT25F4096(W)@VQFPN8 [DX4006]
AT25F4096@SOIC8 [DX1045]
AT25F4096@VQFPN8 [DX4005]

AT25F4096A [DX0001]
AT25F4096A(W)@VQFPN8 [DX4006]
AT25F4096A@VQFPN8 [DX4005]
AT25F512(W)@SOIC8 [DX1044]
AT25F512@SOIC8 [DX1045]
AT25F512A [DX0001]
AT25F512A(W)@VQFPN8 [DX4006]
AT25F512A@VQFPN8 [DX4005]
AT25F512B@UDFN8 [DX4002]
AT25FS010@SOIC8 [DX1045]
AT25FS040@SOIC8 [DX1045]
AT25HP256(W)@VQFPN8 [DX4006]
AT25HP256@SOIC8 [DX1045]
AT25HP512 [DX0001]
AT25HP512@SOIC16 [DX1033]
AT25HP512@VQFPN8 [DX4005]
AT25P1024@VQFPN8 [DX4006]
AT26DF041@SOIC8(4.0) [DX1045]
AT26DF081@SOIC8(4.0) [DX1045#2]
AT26DF081A@SOIC8(4.0) [DX1045#2]
AT26DF161@MLF8 [DX4005#3]
AT26DF161A@MLF8 [DX4005#3]
AT26DF161A@SOIC8(5.4) [DX1031#2]
AT26DF321@MLF8(6*8mm) [DX4006#2]
AT26DF321@SOIC8 [DX1031#2]
AT26F004@SOIC8(4.0) [DX1045#2]
AT27011 [DX0001]
AT27256 [DX0001]
AT27BV010 [DX0001]
AT27BV010@TSOP32 [DX1002]
AT27BV020 [DX0001]
AT27BV020@TSOP32 [DX1002]
AT27BV040 [DX0001]
AT27BV040@TSOP32 [DX1002]
AT27BV1024@PLCC44 [DX2044]
AT27BV256 [DX0001]
AT27BV256@TSOP28 [DX1024]
AT27BV400@PSOP44 [DX1014]
AT27BV4096 [DX0001]
AT27BV4096@VSOP40 [DX1005]
AT27BV512@PLCC32 [DX2032]
AT27BV512@TSOP28 [DX1024]
AT27BV520@TSOP28 [DX1024]
AT27C010 [DX0001]
AT27C010@TSOP32 [DX1002]
AT27C010L@PLCC32 [DX2032]
AT27C020 [DX0001]
AT27C020@TSOP32 [DX1002]
AT25F4096A(W)@SOIC8 [DX1044]
AT25F4096A@SOIC8 [DX1045]
AT25F512 [DX0001]
AT25F512(W)@VQFPN8 [DX4006]
AT25F512@VQFPN8 [DX4005]
AT25F512A(W)@SOIC8 [DX1044]
AT25F512A@SOIC8 [DX1045]
AT25F512B@SOIC8 [DX1045]
AT25FS010@SAP8 [DX4005]
AT25FS040@SAP8 [DX4005]
AT25HP256 [DX0001]
AT25HP256@SOIC16 [DX1033]
AT25HP256@VQFPN8 [DX4005]
AT25HP512(W)@VQFPN8 [DX4006]
AT25HP512@SOIC8 [DX1045]
AT25P1024@SOIC20 [DX1033]
AT26DF041@MLF8 [DX4005]
AT26DF041@SOIC8(5.4) [DX1044]
AT26DF081@SOIC8(5.4) [DX1031#2]
AT26DF081A@SOIC8(5.4) [DX1031#2]
AT26DF161@SOIC8 [DX1031#2]
AT26DF161A@SOIC8(4.0) [DX1045#2]
AT26DF321@MLF8(5*6mm) [DX4005#3]
AT26DF321@SOIC16 [DX1033#2]
AT26F004@MLF8 [DX4005#3]
AT26F004@SOIC8(5.4) [DX1031#2]
AT27011@PLCC32 [DX2032]
AT2732A [DX0001]
AT27BV010@PLCC32 [DX2032]
AT27BV010@VSOP32 [DX1003]
AT27BV020@PLCC32 [DX2032]
AT27BV020@VSOP32 [DX1003]
AT27BV040@PLCC32 [DX2032]
AT27BV040@VSOP32 [DX1003]
AT27BV1024@VSOP40 [DX1005]
AT27BV256@PLCC32 [DX2032]
AT27BV400@PLCC44 [DX2044]
AT27BV400@TSOP48 [DX1004]
AT27BV4096@PLCC44 [DX2044]
AT27BV512 [DX0001]
AT27BV512@SOIC28 [DX1033]
AT27BV520@SOIC20 [DX1033]
AT27BV520@TSSOP20 [DX1000]
AT27C010@PLCC32 [DX2032]
AT27C010L [DX0001]
AT27C010L@TSOP32 [DX1002]
AT27C020@PLCC32 [DX2032]
AT27C040 [DX0001]

AT27C040@PLCC32 [DX2032]
AT27C040@TSOP32 [DX1002]
AT27C080 [DX0001]
AT27C080@PLCC32 [DX2032]
AT27C080@TSOP32 [DX1002]
AT27C1024 [DX0001]
AT27C1024@PLCC44 [DX2044]
AT27C1024@VSOP40 [DX1005]
AT27C1024L [DX0001]
AT27C1024L@PLCC44 [DX2044]
AT27C128 [DX0001]
AT27C128@PLCC32 [DX2032]
AT27C2048 [DX0001]
AT27C2048@PLCC44 [DX2044]
AT27C2048@VSOP40 [DX1005]
AT27C256 [DX0001]
AT27C256@PLCC32 [DX2032]
AT27C256R [DX0001]
AT27C256R@PLCC32 [DX2032]
AT27C256R@SOIC28 [DX1035]
AT27C256R@TSOP28 [DX1024]
AT27C4096 [DX0001]
AT27C4096@PLCC44 [DX2044]
AT27C4096@VSOP40 [DX1005]
AT27C512 [DX0001]
AT27C512@PLCC32 [DX2032]
AT27C512R [DX0001]
AT27C512R@PLCC32 [DX2032]
AT27C512R@SOIC28 [DX1033]
AT27C512R@TSOP28 [DX1024]
AT27C513 [DX0001]
AT27C513@PLCC32 [DX2032]
AT27C513@SOIC28 [DX1033]
AT27C513R@PLCC32 [DX2032]
AT27C513R@SOIC28 [DX1033]
AT27C515 [DX0001]
AT27C515@PLCC32 [DX2032]
AT27C516 [DX0001]
AT27C516@PLCC44 [DX2044]
AT27C516@VSOP40 [DX1005]
AT27C520@SOIC20 [DX1033]
AT27C520@TSOP28 [DX1024]
AT27C520@TSSOP20 [DX1000]
AT27C64 [DX0001]
AT27C800 [DX0001]
AT27C800@PLCC44 [DX2044]
AT27C800@PSOP44 [DX1014]
AT27C800@TSOP48 [DX1004]
AT27HC1024 [DX0001]
AT27HC1024@PLCC44 [DX2044]
AT27HC256 [DX0001]
AT27HC256@PLCC32 [DX2032]
AT27HC256L [DX0001]
AT27HC256L@PLCC32 [DX2032]
AT27HC256R [DX0001]
AT27HC256R@PLCC32 [DX2032]
AT27HC256RL [DX0001]
AT27HC256RL@PLCC32 [DX2032]
AT27HC64 [DX0001]
AT27HC64@PLCC32 [DX2032]
AT27HC641 [DX0001]
AT27HC641@PLCC28 [DX2028]
AT27HC641R [DX0001]
AT27HC641R@PLCC28 [DX2028]
AT27HC642 [DX0001]
AT27HC642@PLCC28 [DX2028]
AT27HC642R [DX0001]
AT27HC642R@PLCC28 [DX2028]
AT27HC64L [DX0001]
AT27HC64L@PLCC32 [DX2032]
AT27LV010 [DX0001]
AT27LV010@PLCC32 [DX2032]
AT27LV010@TSOP32 [DX1002]
AT27LV010@VSOP32 [DX1003]
AT27LV010A [DX0001]
AT27LV010A@PLCC32 [DX2032]
AT27LV010A@TSOP32 [DX1002]
AT27LV010A@VSOP32 [DX1003]
AT27LV020A [DX0001]
AT27LV020A@PLCC32 [DX2032]
AT27LV020A@TSOP32 [DX1002]
AT27LV020A@VSOP32 [DX1003]
AT27LV040 [DX0001]
AT27LV040@PLCC32 [DX2032]
AT27LV040@TSOP32 [DX1002]
AT27LV040@VSOP32 [DX1003]
AT27LV040A [DX0001]
AT27LV040A@PLCC32 [DX2032]
AT27LV040A@TSOP32 [DX1002]
AT27LV040A@VSOP32 [DX1003]
AT27LV1024 [DX0001]
AT27LV1024@PLCC44 [DX2044]
AT27LV1026@PLCC44 [DX2044]
AT27LV1026@TSOP40 [DX1005]
AT27LV256A [DX0001]
AT27LV256A@PLCC32 [DX2032]

AT27LV256A@SOIC28 [DX1035]
AT27LV256A@TSOP28 [DX1024]
AT27LV256R [DX0001]
AT27LV256R@PLCC32 [DX2032]
AT27LV256R@SOIC28 [DX1035]
AT27LV256R@TSOP28 [DX1024]
AT27LV4096 [DX0001]
AT27LV4096@PLCC44 [DX2044]
AT27LV512A [DX0001]
AT27LV512A@PLCC32 [DX2032]
AT27LV512A@SOIC28 [DX1033]
AT27LV512A@TSOP28 [DX1024]
AT27LV512R [DX0001]
AT27LV512R@PLCC32 [DX2032]
AT27LV512R@TSOP28 [DX1024]
AT27LV520@SOIC20 [DX1033]
AT27LV520@TSOP28 [DX1024]
AT27LV520@TSSOP20 [DX1000]
AT27LV800 [DX0001]
AT27LV800@PSOP44 [DX1014]
AT27RW1024@PLCC44 [DX2044]
AT27RW1024@TSOP40 [DX1005]
AT28BV16 [DX0001]
AT28BV16@PLCC32 [DX2032]
AT28BV16@SOIC24 [DX1033]
AT28BV16@TSOP28 [DX1063]
AT28BV256 [DX0001]
AT28BV256@PLCC32 [DX2032]
AT28BV256@SOIC28 [DX1033]
AT28BV256@TSOP28 [DX1024]
AT28BV64 [DX0001]
AT28BV64@PLCC32 [DX2032]
AT28BV64@SOIC28 [DX1033]
AT28BV64@TSOP28 [DX1024]
AT28BV64B [DX0001]
AT28BV64B@PLCC32 [DX2032]
AT28BV64B@SOIC28 [DX1033]
AT28BV64B@TSOP28 [DX1024]
AT28C010 [DX0001]
AT28C010@PLCC32 [DX2032]
AT28C010@PLCC44 [DX2044]
AT28C010@TSOP32 [DX1002]
AT28C010E [DX0001]
AT28C010E@PLCC32 [DX2032]
AT28C010E@PLCC44 [DX2044]
AT28C010E@TSOP32 [DX1002]
AT28C04 [DX0001]
AT28C04@PLCC32 [DX2032]
AT28C040 [DX0001]
AT28C040@PLCC32 [DX2032]
AT28C040@PLCC44 [DX2044]
AT28C040@TSOP48 [DX1004]
AT28C04E [DX0001]
AT28C04E@PLCC32 [DX2032]
AT28C04F [DX0001]
AT28C04F@PLCC32 [DX2032]
AT28C16 [DX0001]
AT28C16@PLCC32 [DX2032]
AT28C16@SOIC24 [DX1033]
AT28C16@TSOP28 [DX1063]
AT28C16E [DX0001]
AT28C16E@PLCC32 [DX2032]
AT28C16F [DX0001]
AT28C16F@PLCC32 [DX2032]
AT28C17 [DX0001]
AT28C17@PLCC32 [DX2032]
AT28C17@SOIC28 [DX1033]
AT28C17E [DX0001]
AT28C17E@PLCC32 [DX2032]
AT28C17F [DX0001]
AT28C17F@PLCC32 [DX2032]
AT28C256 [DX0001]
AT28C256@PLCC32 [DX2032]
AT28C256@SOIC28 [DX1033]
AT28C256@TSOP28 [DX1024]
AT28C256E [DX0001]
AT28C256E@PLCC32 [DX2032]
AT28C256E@SOIC28 [DX1033]
AT28C256E@TSOP28 [DX1024]
AT28C256F [DX0001]
AT28C256F@PLCC32 [DX2032]
AT28C64 [DX0001]
AT28C64@PLCC32 [DX2032]
AT28C64@SOIC28 [DX1033]
AT28C64@TSOP28 [DX1024]
AT28C64B [DX0001]
AT28C64B@PLCC32 [DX2032]
AT28C64B@SOIC28 [DX1033]
AT28C64B@TSOP28 [DX1024]
AT28C64E [DX0001]
AT28C64E@PLCC32 [DX2032]
AT28C64E@TSOP28 [DX1024]
AT28C64F [DX0001]
AT28C64F@PLCC32 [DX2032]
AT28C64F@TSOP28 [DX1024]
AT28C64X [DX0001]

AT28C64X@PLCC32 [DX2032]
AT28C64X@SOIC28 [DX1033]
AT28C64X@TSOP28 [DX1024]
AT28HC04 [DX0001]
AT28HC04@PLCC32 [DX2032]
AT28HC16 [DX0001]
AT28HC16L [DX0001]
AT28HC191 [DX0001]
AT28HC191L [DX0001]
AT28HC256 [DX0001]
AT28HC256@PLCC32 [DX2032]
AT28HC256@TSOP28 [DX1024]
AT28HC256E [DX0001]
AT28HC256E@PLCC32 [DX2032]
AT28HC256F [DX0001]
AT28HC256F@PLCC32 [DX2032]
AT28HC256L [DX0001]
AT28HC256L@PLCC32 [DX2032]
AT28HC256LE [DX0001]
AT28HC256LE@PLCC32 [DX2032]
AT28HC291 [DX0001]
AT28HC291@PLCC28 [DX2028]
AT28HC291L [DX0001]
AT28HC291L@PLCC28 [DX2028]
AT28HC64 [DX0001]
AT28HC64@PLCC32 [DX2032]
AT28HC64@TSOP28 [DX1024]
AT28HC64B [DX0001]
AT28HC64B@PLCC32 [DX2032]
AT28HC64B@SOIC28 [DX1033]
AT28HC64B@TSOP28 [DX1024]
AT28HC64BF [DX0001]
AT28HC64BF@PLCC32 [DX2032]
AT28HC64BF@SOIC28 [DX1033]
AT28HC64BF@TSOP28 [DX1024]
AT28HC64L [DX0001]
AT28HC64L@PLCC32 [DX2032]
AT28HC64L@TSOP28 [DX1024]
AT28LV010 [DX0001]
AT28LV010@PLCC32 [DX2032]
AT28LV010@TSOP32 [DX1002]
AT28LV256 [DX0001]
AT28LV256@PLCC32 [DX2032]
AT28LV256@TSOP28 [DX1024]
AT28LV64 [DX0001]
AT28LV64@PLCC32 [DX2032]
AT28LV64B [DX0001]
AT28LV64B@PLCC32 [DX2032]
AT28LV64B@SOIC28 [DX1033]
AT28LV64B@TSOP28 [DX1024]
AT28MC010 [DX0001]
AT28MC010@PLCC32 [DX2032]
AT28MC010@PLCC44 [DX2044]
AT28MC010@TSOP32 [DX1002]
AT28MC020 [DX0001]
AT28MC020@PLCC32 [DX2032]
AT28MC020@PLCC44 [DX2044]
AT28MC020@TSOP32 [DX1002]
AT28MC040 [DX0001]
AT28MC040@PLCC32 [DX2032]
AT28MC040@PLCC44 [DX2044]
AT28MC040@TSOP32 [DX1002]
AT28PC64 [DX0001]
AT28PC64@PLCC32 [DX2032]
AT28PC64@TSOP28 [DX1024]
AT28PC64E [DX0001]
AT28PC64E@PLCC32 [DX2032]
AT28PC64E@TSOP28 [DX1024]
AT29BV010A@PLCC32 [DX2032]
AT29BV010A@TSOP32 [DX1002]
AT29BV020@PLCC32 [DX2032]
AT29BV020@TSOP32 [DX1002]
AT29BV040A@TSOP32 [DX1002]
AT29C010 [DX0001]
AT29C010@PLCC32 [DX2032]
AT29C010@TSOP32 [DX1002]
AT29C010A [DX0001]
AT29C010A@PLCC32 [DX2032]
AT29C010A@TSOP32 [DX1002]
AT29C020 [DX0001]
AT29C020@PLCC32 [DX2032]
AT29C020@TSOP32 [DX1002]
AT29C040 [DX0001]
AT29C040@PLCC32 [DX2032]
AT29C040@TSOP32 [DX1002]
AT29C040A [DX0001]
AT29C040A@PLCC32 [DX2032]
AT29C040A@TSOP32 [DX1002]
AT29C1024@PLCC44 [DX2044]
AT29C1024@TSOP48 [DX1004]
AT29C256 [DX0001]
AT29C256@PLCC32 [DX2032]
AT29C256@TSOP28 [DX1024]
AT29C257 [DX0001]
AT29C257@PLCC32 [DX2032]
AT29C512 [DX0001]

AT29C512@PLCC32 [DX2032]
AT29C512@TSOP32 [DX1002]
AT29LV010 [DX0001]
AT29LV010@PLCC32 [DX2032]
AT29LV010@TSOP32 [DX1002]
AT29LV010A@PLCC32 [DX2032]
AT29LV010A@TSOP32 [DX1002]
AT29LV020 [DX0001]
AT29LV020@PLCC32 [DX2032]
AT29LV020@TSOP32 [DX1002]
AT29LV040A [DX0001]
AT29LV040A@PLCC32 [DX2032]
AT29LV040A@TSOP32 [DX1002]
AT29LV1024@PLCC44 [DX2044]
AT29LV1024@TSOP48 [DX1004]
AT29LV256 [DX0001]
AT29LV256@PLCC32 [DX2032]
AT29LV256@TSOP28 [DX1024]
AT29LV512 [DX0001]
AT29LV512@PLCC32 [DX2032]
AT29LV512@TSOP32 [DX1002]
AT30TSE002@UDFN8 [DX4002]
AT30TSE002@WDFN8 [DX4002]
AT30TSE004@UDFN8 [DX4002]
AT30TSE004@WDFN8 [DX4002]
AT30TSE752@MSOP8 [DX1015]
AT30TSE752@SOIC8 [DX1045]
AT30TSE752@UDFN8 [DX4002]
AT30TSE754@MSOP8 [DX1015]
AT30TSE754@SOIC8 [DX1045]
AT30TSE754@UDFN8 [DX4002]
AT30TSE758@MSOP8 [DX1015]
AT30TSE758@SOIC8 [DX1045]
AT30TSE758@UDFN8 [DX4002]
AT32C16 [DX0001]
AT32C16@PLCC44
AT34C02 [DX0001]
AT34C02@SOIC8 [DX1045]
AT34C02@TSSOP8 [DX1059]
AT34C02B [DX0001]
AT34C02B@SOIC8 [DX1045]
AT34C02B@TSSOP8 [DX1059]
AT34C02C [DX0001]
AT34C02C@dBGA8 [DX5156]
AT34C02C@MAP8 [DX4047]
AT34C02C@SOIC8 [DX1045]
AT34C02C@TSSOP8 [DX1059]
AT45BCM021D(page256)@SOIC8 [DX1031#1]
AT45D011@PLCC32 [DX2032]
AT45D011@SOIC8 [DX1031]
AT45D011@TSSOP14 [DX1000]
AT45D021@PLCC32 [DX2032]
AT45D021@SOIC28 [DX1035]
AT45D021@TSOP28 [DX1024]
AT45D041@PLCC32 [DX2032]
AT45D041@SOIC28 [DX1035]
AT45D041@TSOP28 [DX1024]
AT45D081@SOIC28 [DX1035]
AT45D081@TSOP32 [DX1002]
AT45D161@PLCC32 [DX2032]
AT45D161@SOIC28 [DX1035]
AT45D161@TSOP28 [DX1024]
AT45DB011@PLCC32 [DX2032]
AT45DB011@SOIC8 [DX1031]
AT45DB011@TSSOP14 [DX1000]
AT45DB011B@PLCC32 [DX2032]
AT45DB011B@SOIC8 [DX1031]
AT45DB011B@TSSOP14 [DX1000]
AT45DB011D@SOIC8 [DX1031-1]
AT45DB011D@SOIC8[150 mil] [DX1016-1]
AT45DB011D@UDFN8 [DX4005-2]
AT45DB021@PLCC32 [DX2032]
AT45DB021@SOIC28 [DX1035]
AT45DB021@TSOP28 [DX1024]
AT45DB021A@PLCC32 [DX2032]
AT45DB021A@SOIC28 [DX1035]
AT45DB021A@TSOP28 [DX1024]
AT45DB021B@CBGA9 [DX50UN]
AT45DB021B@SOIC28 [DX1035]
AT45DB021B@SOIC8 [DX1031]
AT45DB021B@TSOP28 [DX1024]
AT45DB021D@SOIC8 [DX1031-1]
AT45DB021D@SOIC8[150 mil] [DX1016-1]
AT45DB021D@UDFN8 [DX4005-2]
AT45DB021E@SOIC8 [DX1031]
AT45DB021E@SOIC8(256B) [DX1031]
AT45DB021E@SOIC8[150 mil] [DX1016]
AT45DB021E@SOIC8[150 mil](256B) [DX1016]

AT45DB021E@UDFN8 [DX4005]　　AT45DB021E@UDFN8(256B) [DX4005]
AT45DB041@PLCC32 [DX2032]　　AT45DB041@SOIC28 [DX1035]
AT45DB041@TSOP28 [DX1024]　　AT45DB041A@PLCC32 [DX2032]
AT45DB041A@SOIC28 [DX1035]　　AT45DB041A@TSOP28 [DX1024]
AT45DB041B@CASON8 [DX4006]　　AT45DB041B@CBGA14 [DX50UN]
AT45DB041B@SOIC28 [DX1035]　　AT45DB041B@SOIC8 [DX1031]
AT45DB041B@TSOP28 [DX1024]
AT45DB041D(page256)@MLF8 [DX4005#2]
AT45DB041D(page256)@SOIC8[150] [DX1016#1]
AT45DB041D(page256)@SOIC8[200] [DX1031#1]
AT45DB041D(page264)@MLF8 [DX4005-2]
AT45DB041D(page264)@SOIC8[150] [DX1016-1]
AT45DB041D(page264)@SOIC8[200] [DX1031-1]
AT45DB041E(page256)@MLF8 [DX4005#2]
AT45DB041E(page256)@SOIC8[150] [DX1016#1]
AT45DB041E(page256)@SOIC8[200] [DX1031#1]
AT45DB041E(page264)@MLF8 [DX4005-2]
AT45DB041E(page264)@SOIC8[150] [DX1016-1]
AT45DB041E(page264)@SOIC8[200] [DX1031-1]
AT45DB081@SOIC28 [DX1035]　　AT45DB081@TSOP32 [DX1002]
AT45DB081A@PLCC32 [DX2032]　　AT45DB081A@SOIC28 [DX1035]
AT45DB081A@TSOP28 [DX1024]　　AT45DB081B@CASON8 [DX4006]
AT45DB081B@CBGA14 [DX50UN]　　AT45DB081B@SOIC28 [DX1035]
AT45DB081B@SOIC8 [DX1031]　　AT45DB081B@TSOP28 [DX1024]
AT45DB081D(256 byte)@MLF8 [DX4005-2]
AT45DB081D(256 byte)@SOIC8 [DX1031-1]
AT45DB081D(256 byte)@SOIC8[150] [DX1016-1]
AT45DB081D@MLF8 [DX4005-2]　　AT45DB081D@SOIC8 [DX1031-1]
AT45DB081D@SOIC8[150 mil] [DX1016-1]
AT45DB161@PLCC32 [DX2032]　　AT45DB161@SOIC28 [DX1035]
AT45DB161@TSOP28 [DX1024]　　AT45DB161B@CASON8 [DX4006]
AT45DB161B@SOIC28 [DX1035]　　AT45DB161B@TSOP28 [DX1024]
AT45DB161D(page512)@SOIC8 [DX1031-1]
AT45DB161D(page528)@SOIC8 [DX1031-1]
AT45DB161E@QFN8[512B] [DX4005]　　AT45DB161E@QFN8[528B] [DX4005]
AT45DB161E@SOIC8(150 mil)[512B] [DX1016]
AT45DB161E@SOIC8(150 mil)[528B] [DX1016]
AT45DB161E@SOIC8[512B] [DX1031]　　AT45DB161E@SOIC8[528B] [DX1031]
AT45DB321@TSOP32 [DX1002]　　AT45DB321B@SOIC28 [DX1035]
AT45DB321B@TSOP32 [DX1002]　　AT45DB321C@CASON8 [DX4006]
AT45DB321C@SOIC28 [DX1035]　　AT45DB321C@TSOP28 [DX1024]
AT45DB321D@QFN8[5*6mm] [DX4005#2]
AT45DB321D@QFN8[5*6mm][page512] [DX4005#2]
AT45DB321D@QFN8[6*8mm] [DX4006#3]
AT45DB321D@QFN8[6*8mm][page512] [DX4006#3]
AT45DB321D@SOIC8 [DX1031#1]
AT45DB321D@SOIC8[page512] [DX1031#1]
AT45DB321D@TSOP28 [DX1024#1]

AT45DB321D@TSOP28[page512] [DX1024#1]
AT45DB642@TSOP40 [DX1006]
AT45DB642D@CASON8 [DX4006#3]
AT45DB642D@CASON8(ISP) [DX0001]
AT45DB642D@CASON8[page1024] [DX4006-3]
AT45DB642D@TSOP28 [DX1024#1]
AT45DB642D@TSOP28(ISP) [DX0001]
AT45DB642D@TSOP28[page1024] [DX1024-1]
AT49BN1604@TSOP56 [DX1011]
AT49BN1604T@TSOP56 [DX1011]
AT49BV001 [DX0001]
AT49BV001@PLCC32 [DX2032]
AT49BV001@TSOP32 [DX1002]
AT49BV001@VSOP32 [DX1003]
AT49BV001A [DX0001]
AT49BV001A@PLCC32 [DX2032]
AT49BV001A@TSOP32 [DX1002]
AT49BV001A@VSOP32 [DX1003]
AT49BV001AN [DX0001]
AT49BV001AN@PLCC32 [DX2032]
AT49BV001AN@TSOP32 [DX1002]
AT49BV001AN@VSOP32 [DX1003]
AT49BV001ANT [DX0001]
AT49BV001ANT@PLCC32 [DX2032]
AT49BV001ANT@TSOP32 [DX1002]
AT49BV001ANT@VSOP32 [DX1003]
AT49BV001AT [DX0001]
AT49BV001AT@PLCC32 [DX2032]
AT49BV001AT@TSOP32 [DX1002]
AT49BV001AT@VSOP32 [DX1003]
AT49BV001N [DX0001]
AT49BV001N@PLCC32 [DX2032]
AT49BV001N@TSOP32 [DX1002]
AT49BV001N@VSOP32 [DX1003]
AT49BV001NT [DX0001]
AT49BV001NT@PLCC32 [DX2032]
AT49BV001NT@TSOP32 [DX1002]
AT49BV001NT@VSOP32 [DX1003]
AT49BV001T [DX0001]
AT49BV001T@PLCC32 [DX2032]
AT49BV001T@TSOP32 [DX1002]
AT49BV001T@VSOP32 [DX1003]
AT49BV002 [DX0001]
AT49BV002@PLCC32 [DX2032]
AT49BV002@TSOP32 [DX1002]
AT49BV002@VSOP32 [DX1003]
AT49BV002A [DX0001]
AT49BV002A@PLCC32 [DX2032]
AT49BV002A@TSOP32 [DX1002]
AT49BV002A@VSOP32 [DX1003]
AT49BV002AN [DX0001]
AT49BV002AN@PLCC32 [DX2032]
AT49BV002AN@TSOP32 [DX1002]
AT49BV002AN@VSOP32 [DX1003]
AT49BV002ANT [DX0001]
AT49BV002ANT@PLCC32 [DX2032]
AT49BV002ANT@TSOP32 [DX1002]
AT49BV002ANT@VSOP32 [DX1003]
AT49BV002AT [DX0001]
AT49BV002AT@PLCC32 [DX2032]
AT49BV002AT@TSOP32 [DX1002]
AT49BV002AT@VSOP32 [DX1003]
AT49BV002N [DX0001]
AT49BV002N@PLCC32 [DX2032]
AT49BV002N@TSOP32 [DX1002]
AT49BV002N@VSOP32 [DX1003]
AT49BV002NT [DX0001]
AT49BV002NT@PLCC32 [DX2032]
AT49BV002NT@TSOP32 [DX1002]
AT49BV002NT@VSOP32 [DX1003]
AT49BV002T [DX0001]
AT49BV002T@PLCC32 [DX2032]
AT49BV002T@TSOP32 [DX1002]
AT49BV002T@VSOP32 [DX1003]
AT49BV008@TSOP40 [DX1006]
AT49BV008A@TSOP40 [DX1006]
AT49BV008A@uBGA48 [DX5031]
AT49BV008AT@TSOP40 [DX1006]
AT49BV008AT@uBGA48 [DX5031]
AT49BV010 [DX0001]
AT49BV010@PLCC32 [DX2032]
AT49BV010@TSOP32 [DX1002]
AT49BV010@VSOP32 [DX1003]
AT49BV020 [DX0001]
AT49BV020@PLCC32 [DX2032]
AT49BV020@TSOP32 [DX1002]
AT49BV020@VSOP32 [DX1003]
AT49BV040 [DX0001]
AT49BV040@PLCC32 [DX2032]
AT49BV040@TSOP32 [DX1002]
AT49BV040@VSOP32 [DX1003]
AT49BV040A@PLCC32 [DX2032]

AT49BV040A@TSOP32 [DX1002]
AT49BV040A@VSOP32 [DX1003]
AT49BV040B@PLCC32 [DX2032]
AT49BV040B@TSOP32 [DX1002]
AT49BV040B@VSOP32 [DX1003]
AT49BV040T [DX0001]
AT49BV040T@PLCC32 [DX2032]
AT49BV040T@TSOP32 [DX1002]
AT49BV040T@VSOP32 [DX1003]
AT49BV080@PSOP44 [DX1014]
AT49BV080@TSOP40 [DX1006]
AT49BV080T@PSOP44 [DX1014]
AT49BV080T@TSOP40 [DX1006]
AT49BV1024A@TSOP40 [DX1005]
AT49BV160@TSOP48 [DX1004]
AT49BV160@uBGA48 [DX5080]
AT49BV1604@TSOP48 [DX1004]
AT49BV1604@uBGA48 [DX5080]
AT49BV1604A@TSOP48 [DX1004]
AT49BV1604A@uBGA48 [DX5080]
AT49BV1604AT@TSOP48 [DX1004]
AT49BV1604AT@uBGA48 [DX5080]
AT49BV1604T@TSOP48 [DX1004]
AT49BV1604T@uBGA48 [DX5080]
AT49BV160C@TSOP48 [DX1004]
AT49BV160C@uBGA48 [DX50UN]
AT49BV160CT@TSOP48 [DX1004]
AT49BV160CT@uBGA48 [DX50UN]
AT49BV160D@TSOP48 [DX1004]
AT49BV160DT@TSOP48 [DX1004]
AT49BV160S@FBGA64 [DX5100]
AT49BV160ST@FBGA64 [DX5100]
AT49BV160T@TSOP48 [DX1004]
AT49BV160T@uBGA48 [DX5080]
AT49BV161@CBGA48 [DX5002]
AT49BV161@TSOP48 [DX1004]
AT49BV1614@CBGA48 [DX5005]
AT49BV1614@TSOP48 [DX1004]
AT49BV1614A@CBGA48 [DX5002]
AT49BV1614A@TSOP48 [DX1004]
AT49BV1614AT@CBGA48 [DX5002]
AT49BV1614AT@TSOP48 [DX1004]
AT49BV1614T@CBGA48 [DX5005]
AT49BV1614T@TSOP48 [DX1004]
AT49BV1618@CBGA48 [DX5005]
AT49BV1618@TSOP48 [DX1004]
AT49BV1618T@CBGA48 [DX5005]
AT49BV1618T@TSOP48 [DX1004]
AT49BV161T@CBGA48 [DX5002]
AT49BV161T@TSOP48 [DX1004]
AT49BV162A@CBGA48 [DX5025]
AT49BV162A@TSOP48 [DX1004]
AT49BV162AT@CBGA48 [DX5025]
AT49BV162AT@TSOP48 [DX1004]
AT49BV163A@CBGA48 [DX5002]
AT49BV163A@TSOP48 [DX1004]
AT49BV163AT@CBGA48 [DX5002]
AT49BV163AT@TSOP48 [DX1004]
AT49BV163D@FBGA48 [DX5002]
AT49BV163D@TSOP48 [DX1004]
AT49BV163DT@FBGA48 [DX5002]
AT49BV163DT@TSOP48 [DX1004]
AT49BV2048@PSOP44 [DX1014]
AT49BV2048@TSOP48 [DX1004]
AT49BV2048A@PSOP44 [DX1014]
AT49BV2048A@TSOP48 [DX1004]
AT49BV2048B@TSOP48 [DX1004]
AT49BV320@TSOP48 [DX1004]
AT49BV320@uBGA48 [DX50UN]
AT49BV320A@CBGA48 [DX5078]
AT49BV320A@TSOP48 [DX1004]
AT49BV320AT@CBGA48 [DX5078]
AT49BV320AT@TSOP48 [DX1004]
AT49BV320C@TSOP48 [DX1004]
AT49BV320C@uBGA48 [DX5078]
AT49BV320CT@TSOP48 [DX1004]
AT49BV320CT@uBGA48 [DX5078]
AT49BV320D@FBGA48 [DX5078]
AT49BV320D@TSOP48 [DX1004]
AT49BV320DT@FBGA48 [DX5078]
AT49BV320DT@TSOP48 [DX1004]
AT49BV320S@FBGA64 [DX5100]
AT49BV320ST@FBGA64 [DX5100]
AT49BV320T@TSOP48 [DX1004]
AT49BV320T@uBGA48 [DX50UN]
AT49BV321@CBGA48 [DX5001]
AT49BV321@TSOP48 [DX1004]
AT49BV3214T@CBGA48 [DX5005]
AT49BV3214T@TSOP48 [DX1004]
AT49BV3218@CBGA48 [DX5005]
AT49BV3218@TSOP48 [DX1004]
AT49BV3218T@CBGA48 [DX5005]
AT49BV3218T@TSOP48 [DX1004]
AT49BV321T@CBGA48 [DX5001]
AT49BV321T@TSOP48 [DX1004]
AT49BV322A@FBGA48 [DX5025]

AT49BV322A@TSOP48 [DX1004]
AT49BV322AT@TSOP48 [DX1004]
AT49BV322D@TSOP48 [DX1004]
AT49BV322DT@TSOP48 [DX1004]
AT49BV4096@TSOP48 [DX1004]
AT49BV4096A@TSOP48 [DX1004]
AT49BV512 [DX0001]
AT49BV512@TSOP32 [DX1002]
AT49BV640D@FBGA48 [DX5078]
AT49BV640DT@FBGA48 [DX5078]
AT49BV640S@FBGA64 [DX5100]
AT49BV6416@TSOP48 [DX1004]
AT49BV642D@TSOP48 [DX1004]
AT49BV8004@CBGA48 [DX5050]
AT49BV8004T@CBGA48 [DX5050]
AT49BV8011@CBGA48 [DX5050]
AT49BV8011T@CBGA48 [DX5050]
AT49BV802A@CBGA48 [DX5002]
AT49BV802AT@CBGA48 [DX5002]
AT49BV802D@CBGA48 [DX5002]
AT49BV802DT@CBGA48 [DX5002]
AT49BV8192@PSOP44 [DX1014]
AT49BV8192A@PSOP44 [DX1014]
AT49BV8192A@uBGA48 [DX50UN]
AT49BV8192AT@TSOP48 [DX1004]
AT49BV8192T@PSOP44 [DX1014]
AT49F001 [DX0001]
AT49F001@TSOP32 [DX1002]
AT49F001A [DX0001]
AT49F001A@TSOP32 [DX1002]
AT49F001AN [DX0001]
AT49F001AN@TSOP32 [DX1002]
AT49F001ANT [DX0001]
AT49F001ANT@TSOP32 [DX1002]
AT49F001AT [DX0001]
AT49F001AT@TSOP32 [DX1002]
AT49F001N [DX0001]
AT49F001N@TSOP32 [DX1002]
AT49F001NT [DX0001]
AT49F001NT@TSOP32 [DX1002]
AT49F001T [DX0001]
AT49F001T@TSOP32 [DX1002]
AT49F002 [DX0001]
AT49F002@TSOP32 [DX1002]
AT49F002A [DX0001]
AT49F002A@TSOP32 [DX1002]
AT49F002AN [DX0001]
AT49F002AN@TSOP32 [DX1002]
AT49BV322AT@FBGA48 [DX5025]
AT49BV322D@FBGA48 [DX5025]
AT49BV322DT@FBGA48 [DX5025]
AT49BV4096@PSOP44 [DX1014]
AT49BV4096A@PSOP44 [DX1014]
AT49BV4096A@uBGA48 [DX50UN]
AT49BV512@PLCC32 [DX2032]
AT49BV512@VSOP32 [DX1003]
AT49BV640D@TSOP56 [DX1011]
AT49BV640DT@TSOP56 [DX1011]
AT49BV640ST@FBGA64 [DX5100]
AT49BV6416T@TSOP48 [DX1004]
AT49BV642DT@TSOP48 [DX1004]
AT49BV8004@TSOP48 [DX1004]
AT49BV8004T@TSOP48 [DX1004]
AT49BV8011@TSOP48 [DX1004]
AT49BV8011T@TSOP48 [DX1004]
AT49BV802A@TSOP48 [DX1004]
AT49BV802AT@TSOP48 [DX1004]
AT49BV802D@TSOP48 [DX1004]
AT49BV802DT@TSOP48 [DX1004]
AT49BV8192@TSOP48 [DX1004]
AT49BV8192A@TSOP48 [DX1004]
AT49BV8192AT@PSOP44 [DX1014]
AT49BV8192AT@uBGA48 [DX50UN]
AT49BV8192T@TSOP48 [DX1004]
AT49F001@PLCC32 [DX2032]
AT49F001@VSOP32 [DX1003]
AT49F001A@PLCC32 [DX2032]
AT49F001A@VSOP32 [DX1003]
AT49F001AN@PLCC32 [DX2032]
AT49F001AN@VSOP32 [DX1003]
AT49F001ANT@PLCC32 [DX2032]
AT49F001ANT@VSOP32 [DX1003]
AT49F001AT@PLCC32 [DX2032]
AT49F001AT@VSOP32 [DX1003]
AT49F001N@PLCC32 [DX2032]
AT49F001N@VSOP32 [DX1003]
AT49F001NT@PLCC32 [DX2032]
AT49F001NT@VSOP32 [DX1003]
AT49F001T@PLCC32 [DX2032]
AT49F001T@VSOP32 [DX1003]
AT49F002@PLCC32 [DX2032]
AT49F002@VSOP32 [DX1003]
AT49F002A@PLCC32 [DX2032]
AT49F002A@VSOP32 [DX1003]
AT49F002AN@PLCC32 [DX2032]
AT49F002AN@VSOP32 [DX1003]

AT49F002ANT [DX0001]
AT49F002ANT@PLCC32 [DX2032]
AT49F002ANT@TSOP32 [DX1002]
AT49F002ANT@VSOP32 [DX1003]
AT49F002AT [DX0001]
AT49F002AT@PLCC32 [DX2032]
AT49F002AT@TSOP32 [DX1002]
AT49F002AT@VSOP32 [DX1003]
AT49F002N [DX0001]
AT49F002N@PLCC32 [DX2032]
AT49F002N@TSOP32 [DX1002]
AT49F002N@VSOP32 [DX1003]
AT49F002NT [DX0001]
AT49F002NT@PLCC32 [DX2032]
AT49F002NT@TSOP32 [DX1002]
AT49F002NT@VSOP32 [DX1003]
AT49F002T [DX0001]
AT49F002T@PLCC32 [DX2032]
AT49F002T@TSOP32 [DX1002]
AT49F002T@VSOP32 [DX1003]
AT49F008@TSOP40 [DX1006]
AT49F008A@TSOP40 [DX1006]
AT49F008AT@TSOP40 [DX1006]
AT49F010 [DX0001]
AT49F010@PLCC32 [DX2032]
AT49F010@TSOP32 [DX1002]
AT49F020 [DX0001]
AT49F020@PLCC32 [DX2032]
AT49F020@TSOP32 [DX1002]
AT49F040 [DX0001]
AT49F040@PLCC32 [DX2032]
AT49F040@TSOP32 [DX1002]
AT49F040A [DX0001]
AT49F040A@PLCC32 [DX2032]
AT49F040A@TSOP32 [DX1002]
AT49F040T [DX0001]
AT49F040T@PLCC32 [DX2032]
AT49F040T@TSOP32 [DX1002]
AT49F080@PSOP44 [DX1014]
AT49F080@TSOP40 [DX1006]
AT49F080T@PSOP44 [DX1014]
AT49F080T@TSOP40 [DX1006]
AT49F1024@TSOP40 [DX1005]
AT49F1024A@TSOP40 [DX1005]
AT49F1025@PLCC44 [DX2044]
AT49F1025@TSOP40 [DX1005]
AT49F1604@TSOP48 [DX1004]
AT49F1604@uBGA48 [DX50UN]
AT49F1604T@TSOP48 [DX1004]
AT49F1604T@uBGA48 [DX50UN]
AT49F1614@CBGA48 [DX5005]
AT49F1614@TSOP48 [DX1004]
AT49F1614T@CBGA48 [DX5005]
AT49F1614T@TSOP48 [DX1004]
AT49F2048@PSOP44 [DX1014]
AT49F2048@TSOP48 [DX1004]
AT49F2048A@PSOP44 [DX1014]
AT49F2048A@TSOP48 [DX1004]
AT49F4096@PSOP44 [DX1014]
AT49F4096@TSOP48 [DX1004]
AT49F4096A@CBGA48 [DX5002]
AT49F4096A@PSOP44 [DX1014]
AT49F4096A@TSOP48 [DX1004]
AT49F4096A@uBGA48 [DX50UN]
AT49F512 [DX0001]
AT49F512@PLCC32 [DX2032]
AT49F512@TSOP32 [DX1002]
AT49F512@VSOP32 [DX1003]
AT49F516@PLCC44 [DX2044]
AT49F516@TSOP40 [DX1005]
AT49F8004@CBGA48 [DX5050]
AT49F8004@TSOP48 [DX1004]
AT49F8004T@CBGA48 [DX5050]
AT49F8004T@TSOP48 [DX1004]
AT49F8011@CBGA48 [DX5050]
AT49F8011@TSOP48 [DX1004]
AT49F8011T@CBGA48 [DX5050]
AT49F8011T@TSOP48 [DX1004]
AT49F8192@PSOP44 [DX1014]
AT49F8192@TSOP48 [DX1004]
AT49F8192A@PSOP44 [DX1014]
AT49F8192A@TSOP48 [DX1004]
AT49F8192AT@PSOP44 [DX1014]
AT49F8192AT@TSOP48 [DX1004]
AT49F8192T@PSOP44 [DX1014]
AT49F8192T@TSOP48 [DX1004]
AT49HBV010 [DX0001]
AT49HBV010@PLCC32 [DX2032]
AT49HBV010@TSOP32 [DX1002]
AT49HBV010@VSOP32 [DX1003]
AT49HF010 [DX0001]
AT49HF010@PLCC32 [DX2032]
AT49HF010@TSOP32 [DX1002]
AT49HLV010 [DX0001]
AT49HLV010@PLCC32 [DX2032]
AT49HLV010@TSOP32 [DX1002]

AT49HLV010@VSOP32 [DX1003]
AT49LH002@TSOP40 [DX1006]
AT49LH004@TSOP40 [DX1006]
AT49LH00B4@TSOP40 [DX1006]
AT49LL020@TSOP40 [DX1006]
AT49LL040@TSOP40 [DX1006]
AT49LL080@TSOP40 [DX1006]
AT49LV001@PLCC32 [DX2032]
AT49LV001@VSOP32 [DX1003]
AT49LV001N@PLCC32 [DX2032]
AT49LV001N@VSOP32 [DX1003]
AT49LV001NT@PLCC32 [DX2032]
AT49LV001NT@VSOP32 [DX1003]
AT49LV001T@PLCC32 [DX2032]
AT49LV001T@VSOP32 [DX1003]
AT49LV002@PLCC32 [DX2032]
AT49LV002@VSOP32 [DX1003]
AT49LV002N@PLCC32 [DX2032]
AT49LV002N@VSOP32 [DX1003]
AT49LV002NT@PLCC32 [DX2032]
AT49LV002NT@VSOP32 [DX1003]
AT49LV002T@PLCC32 [DX2032]
AT49LV002T@VSOP32 [DX1003]
AT49LV008A@TSOP40 [DX1006]
AT49LV008AT@TSOP40 [DX1006]
AT49LV010 [DX0001]
AT49LV010@TSOP32 [DX1002]
AT49LV020 [DX0001]
AT49LV020@TSOP32 [DX1002]
AT49LV040 [DX0001]
AT49LV040@TSOP32 [DX1002]
AT49LV040T [DX0001]
AT49LV040T@TSOP32 [DX1002]
AT49LV080@PSOP44 [DX1014]
AT49LV080T@PSOP44 [DX1014]
AT49LV1024@TSOP40 [DX1005]
AT49LV1025@PLCC44 [DX2044]
AT49LV1604@TSOP48 [DX1004]
AT49LV1604T@TSOP48 [DX1004]
AT49LV160T@TSOP48 [DX1004]
AT49LV161@TSOP48 [DX1004]
AT49LV1614@TSOP48 [DX1004]
AT49LV1614A@TSOP48 [DX1004]
AT49LV1614AT@TSOP48 [DX1004]
AT49LV1614T@TSOP48 [DX1004]
AT49LV161T@TSOP48 [DX1004]
AT49LV2048@TSOP48 [DX1004]
AT49LV2048A@TSOP48 [DX1004]
AT49LH002@PLCC32 [DX2032]
AT49LH004@PLCC32 [DX2032]
AT49LH00B4@PLCC32 [DX2032]
AT49LL020@PLCC32 [DX2032]
AT49LL040@PLCC32 [DX2032]
AT49LL080@PLCC32 [DX2032]
AT49LV001 [DX0001]
AT49LV001@TSOP32 [DX1002]
AT49LV001N [DX0001]
AT49LV001N@TSOP32 [DX1002]
AT49LV001NT [DX0001]
AT49LV001NT@TSOP32 [DX1002]
AT49LV001T [DX0001]
AT49LV001T@TSOP32 [DX1002]
AT49LV002 [DX0001]
AT49LV002@TSOP32 [DX1002]
AT49LV002N [DX0001]
AT49LV002N@TSOP32 [DX1002]
AT49LV002NT [DX0001]
AT49LV002NT@TSOP32 [DX1002]
AT49LV002T [DX0001]
AT49LV002T@TSOP32 [DX1002]
AT49LV008@TSOP40 [DX1006]
AT49LV008A@uBGA48 [DX5031]
AT49LV008AT@uBGA48 [DX5031]
AT49LV010@PLCC32 [DX2032]
AT49LV010@VSOP32 [DX1003]
AT49LV020@PLCC32 [DX2032]
AT49LV020@VSOP32 [DX1003]
AT49LV040@PLCC32 [DX2032]
AT49LV040@VSOP32 [DX1003]
AT49LV040T@PLCC32 [DX2032]
AT49LV040T@VSOP32 [DX1003]
AT49LV080@TSOP40 [DX1006]
AT49LV080T@TSOP40 [DX1006]
AT49LV1024A@TSOP40 [DX1005]
AT49LV160@TSOP48 [DX1004]
AT49LV1604@uBGA48 [DX5080]
AT49LV1604T@uBGA48 [DX5080]
AT49LV161@CBGA48 [DX5002]
AT49LV1614@CBGA48 [DX5005]
AT49LV1614A@CBGA48 [DX5002]
AT49LV1614AT@CBGA48 [DX5002]
AT49LV1614T@CBGA48 [DX5005]
AT49LV161T@CBGA48 [DX5002]
AT49LV2048@PSOP44 [DX1014]
AT49LV2048A@PSOP44 [DX1014]
AT49LV2048B@TSOP48 [DX1004]

AT49LV320@TSOP48 [DX1004]
AT49LV320T@TSOP48 [DX1004]
AT49LV321@CBGA48 [DX5001]
AT49LV3218@CBGA48 [DX5005]
AT49LV3218T@CBGA48 [DX5005]
AT49LV321T@CBGA48 [DX5001]
AT49LV4096A@CBGA48 [DX5002]
AT49LV4096A@TSOP48 [DX1004]
AT49LV8011@CBGA48 [DX5050]
AT49LV8011T@CBGA48 [DX5050]
AT49LV8192@PSOP44 [DX1014]
AT49LV8192A@PSOP44 [DX1014]
AT49LV8192A@uBGA48 [DX50UN]
AT49LV8192AT@TSOP48 [DX1004]
AT49LV8192T@PSOP44 [DX1014]
AT49LW040@PLCC32 [DX2032]
AT49LW080@PLCC32 [DX2032]
AT49SV163D@CBGA48 [DX5025]
AT49SV163DT@CBGA48 [DX5025]
AT49SV322A@CBGA48 [DX5025]
AT49SV322AT@CBGA48 [DX5025]
AT49SV322D@FBGA48 [DX5025]
AT49SV322DT@FBGA48 [DX5025]
AT49SV802A@CBGA48 [DX5002]
AT49SV802AT@CBGA48 [DX5002]
AT52BC1660A@FBGA66 [DX5005]
AT52BC1661A@FBGA66 [DX5005]
AT52BC1661D@FBGA66 [DX5005]
AT52BC3221A@FBGA66 [DX5005]
AT52BC3221D@FBGA66 [DX5005]
AT52BC6402A@FBGA66 [DX5001]
AT52BR1662@CBGA66 [DX5005]
AT52BR1662AT@CBGA66 [DX5005]
AT52BR1664@CBGA66 [DX5005]
AT52BR1664AT@CBGA66 [DX5005]
AT52BR1672@CBGA66 [DX5005]
AT52BR1674@CBGA66 [DX5005]
AT52BR3218A@CBGA66 [DX5005]
AT52BR3224A@CBGA66 [DX5005]
AT52BR3228A@CBGA66 [DX5005]
AT52BR3244@CBGA66 [DX5001]
AT52BR3248@CBGA66 [DX5001]
AT52BR6408A@CSP66 [DX5001]
AT59C11 [DX0001]
AT59C12 [DX0001]
AT59C13 [DX0001]
AT59C22 [DX0001]
AT88SC0104 [DX0001-1]
AT49LV320@uBGA48 [DX50UN]
AT49LV320T@uBGA48 [DX50UN]
AT49LV321@TSOP48 [DX1004]
AT49LV3218@TSOP48 [DX1004]
AT49LV3218T@TSOP48 [DX1004]
AT49LV321T@TSOP48 [DX1004]
AT49LV4096A@PSOP44 [DX1014]
AT49LV4096A@uBGA48 [DX50UN]
AT49LV8011@TSOP48 [DX1004]
AT49LV8011T@TSOP48 [DX1004]
AT49LV8192@TSOP48 [DX1004]
AT49LV8192A@TSOP48 [DX1004]
AT49LV8192AT@PSOP44 [DX1014]
AT49LV8192AT@uBGA48 [DX50UN]
AT49LV8192T@TSOP48 [DX1004]
AT49LW040@TSOP40 [DX1006]
AT49LW080@TSOP40 [DX1006]
AT49SV163D@TSOP48 [DX1004]
AT49SV163DT@TSOP48 [DX1004]
AT49SV322A@TSOP48 [DX1004]
AT49SV322AT@TSOP48 [DX1004]
AT49SV322D@TSOP48 [DX1004]
AT49SV322DT@TSOP48 [DX1004]
AT49SV802A@TSOP48 [DX1004]
AT49SV802AT@TSOP48 [DX1004]
AT52BC1660AT@FBGA66 [DX5005]
AT52BC1661AT@FBGA66 [DX5005]
AT52BC1661DT@FBGA66 [DX5005]
AT52BC3221AT@FBGA66 [DX5005]
AT52BC3221DT@FBGA66 [DX5005]
AT52BC6402AT@FBGA66 [DX5001]
AT52BR1662A@CBGA66 [DX5005]
AT52BR1662T@CBGA66 [DX5005]
AT52BR1664A@CBGA66 [DX5005]
AT52BR1664T@CBGA66 [DX5005]
AT52BR1672T@CBGA66 [DX5005]
AT52BR1674T@CBGA66 [DX5005]
AT52BR3218AT@CBGA66 [DX5005]
AT52BR3224AT@CBGA66 [DX5005]
AT52BR3228AT@CBGA66 [DX5005]
AT52BR3244T@CBGA66 [DX5001]
AT52BR3248T@CBGA66 [DX5001]
AT52BR6408AT@CSP66 [DX5001]
AT59C11@SOIC8 [DX1045]
AT59C12@SOIC8 [DX1045]
AT59C13@SOIC8 [DX1045]
AT59C22@SOIC8 [DX1045]
AT88SC0104@SOIC8 [DX1016-2]

AT88SC0204 [DX0001-1]
AT88SC0204@SOIC8 [DX1016-2]
AT88SC0404@SOIC8 [DX1016-2]
AT88SC0808@SOIC8 [DX1016-2]
AT88SC0808C@SOIC8(FULL) [DX1016-2]
AT93C46(08bit) [DX0001]
AT93C46(08bit)@SOIC8 [DX1045]
AT93C46(08bit)@TSSOP8 [DX1059]
AT93C46(16bit) [DX0001]
AT93C46(16bit)@SOIC8 [DX1045]
AT93C46(16bit)@TSSOP8 [DX1059]
AT93C46A [DX0001]
AT93C46A@SOIC8 [DX1045]
AT93C46A@TSSOP8 [DX1059]
AT93C46C [DX0001]
AT93C46C@SOIC8 [DX1045]
AT93C46C@TSSOP8 [DX1059]
AT93C46D(08bit) [DX0001]
AT93C46D(08bit)@dBGA8 [DX5156]
AT93C46D(08bit)@MAP8 [DX4002]
AT93C46D(08bit)@SOIC8 [DX1045]
AT93C46D(08bit)@TSSOP8 [DX1059]
AT93C46D(16bit) [DX0001]
AT93C46D(16bit)@dBGA8 [DX5156]
AT93C46D(16bit)@MAP8 [DX4002]
AT93C46D(16bit)@SOIC8 [DX1045]
AT93C46D(16bit)@TSSOP8 [DX1059]
AT93C46E [DX0001]
AT93C46E@SOIC8 [DX1045]
AT93C46E@TSSOP8 [DX1059]
AT93C56(08bit) [DX0001]
AT93C56(08bit)@SOIC8 [DX1045]
AT93C56(16bit) [DX0001]
AT93C56(16bit)@SOIC8 [DX1045]
AT93C56A(08bit) [DX0001]
AT93C56A(08bit)@SOIC8 [DX1045]
AT93C56A(08bit)@TSSOP8 [DX1059]
AT93C56A(08bit)@UDFN8 [DX4002]
AT93C56A(16bit) [DX0001]
AT93C56A(16bit)@SOIC8 [DX1045]
AT93C56A(16bit)@TSSOP8 [DX1059]
AT93C56AW(08bit)@SOIC8 [DX1044]
AT93C56AW(16bit)@SOIC8 [DX1044]
AT93C56B(08bit) [DX0001]
AT93C56B(08bit)@SOIC8 [DX1045]
AT93C56B(08bit)@TSSOP8 [DX1059]
AT93C56B(08bit)@UDFN8 [DX4002]
AT93C56B(08bit)@VFNGA8 [DX5156]
AT93C56B(08bit)@XDFN8 [DX0001]
AT93C56B(16bit) [DX0001]
AT93C56B(16bit)@SOIC8 [DX1045]
AT93C56B(16bit)@TSSOP8 [DX1059]
AT93C56B(16bit)@UDFN8 [DX4002]
AT93C56B(16bit)@VFNGA8 [DX5156]
AT93C56B(16bit)@XDFN8 [DX0001]
AT93C57 [DX0001]
AT93C57@SOIC8 [DX1045]
AT93C66(08bit) [DX0001]
AT93C66(08bit)@SOIC8 [DX1045]
AT93C66(16bit) [DX0001]
AT93C66(16bit)@SOIC8 [DX1045]
AT93C66A(08bit) [DX0001]
AT93C66A(08bit)@SOIC8 [DX1045]
AT93C66A(08bit)@TSSOP8 [DX1059]
AT93C66A(16bit) [DX0001]
AT93C66A(16bit)@SOIC8 [DX1045]
AT93C66A(16bit)@TSSOP8 [DX1059]
AT93C66A(16bit)@UDFN8 [DX4002]
AT93C66AW(08bit)@SOIC8 [DX1044]
AT93C66AW(16bit)@SOIC8 [DX1044]
AT93C66B(08bit) [DX0001]
AT93C66B(08bit)@SOIC8 [DX1045]
AT93C66B(08bit)@TSSOP8 [DX1059]
AT93C66B(08bit)@UDFN8 [DX4002]
AT93C66B(08bit)@VFNGA8 [DX5156]
AT93C66B(08bit)@XDFN8 [DX0001]
AT93C66B(16bit) [DX0001]
AT93C66B(16bit)@SOIC8 [DX1045]
AT93C66B(16bit)@TSSOP8 [DX1059]
AT93C66B(16bit)@UDFN8 [DX4002]
AT93C66B(16bit)@VFNGA8 [DX5156]
AT93C66B(16bit)@XDFN8 [DX0001]
AT93C86(08bit) [DX0001]
AT93C86(08bit)@SOIC8 [DX1045]
AT93C86(08bit)@TSSOP8 [DX1059]
AT93C86(16bit) [DX0001]
AT93C86(16bit)@SOIC8 [DX1045]
AT93C86(16bit)@TSSOP8 [DX1059]
AT93C86A(08bit) [DX0001]
AT93C86A(08bit)@SOIC8 [DX1045]
AT93C86A(08bit)@TSSOP8 [DX1059]
AT93C86A(16bit) [DX0001]
AT93C86A(16bit)@SOIC8 [DX1045]
AT93C86A(16bit)@TSSOP8 [DX1059]
NS0001@SOIC8 [DX1016-2]

DRAM & SRAM

AT3864L [DX0001]
AT38H256 [DX0001]
AT3864L@TSOP28 [DX1001]
AT38H256@TSOP28 [DX1001]

PLD

AT22LV10 [DX0001]
AT22LV10L [DX0001]
AT22V10 [DX0001]
AT22V10L [DX0001]
ATF1500A@PLCC44 [DX2044]
ATF1500ABV@PLCC44 [DX2044]
ATF1500ABVL@PLCC44 [DX2044]
ATF1500AL@PLCC44 [DX2044]
ATF1502AS@PLCC44 [DX2044]
ATF1502AS@TQFP44 [DX3003]
ATF1502ASL@PQFP44 [DX3002]
ATF1502ASV@PLCC44 [DX2044]
ATF1502ASV@TQFP44 [DX3003]
ATF1502ASVL@PQFP44 [DX3002]
ATF1504AS@PLCC44 [DX2044]
ATF1504AS@PLCC84 [DX2084]
ATF1504AS@TQFP100 [DX3021]
ATF1504ASL@PLCC44 [DX2044]
ATF1504ASL@PLCC84 [DX2084]
ATF1504ASL@TQFP100 [DX3021]
ATF1504ASV@PLCC44 [DX2044]
ATF1504ASV@PLCC84 [DX2084]
ATF1504ASV@TQFP100 [DX3021]
ATF1504ASVL@PLCC44 [DX2044]
ATF1504ASVL@PLCC84 [DX2084]
ATF1504ASVL@TQFP100 [DX3021]
ATF1508@PLCC68 [DX2068]
ATF1508@PQFP100 [DX3022]
ATF1508AS@PLCC68 [DX2068]
ATF1508AS@PQFP100 [DX3022]
ATF1508ASL@PLCC68 [DX2068]
ATF1508ASL@PQFP100 [DX3022]
ATF1508ASV@PLCC68 [DX2068]
ATF1508ASV@PQFP100 [DX3022]
ATF1508ASVL@PLCC68 [DX2068]
ATF1508ASVL@PQFP100 [DX3022]
ATF16LV8C [DX0001]
ATF16LV8C@SOIC20 [DX1033]
ATF1500A@TQFP44 [DX3003]
ATF1500ABV@TQFP44 [DX3003]
ATF1500ABVL@TQFP44 [DX3003]
ATF1500AL@TQFP44 [DX3003]
ATF1502AS@PQFP44 [DX3002]
ATF1502ASL@PLCC44 [DX2044]
ATF1502ASL@TQFP44 [DX3003]
ATF1502ASV@PQFP44 [DX3002]
ATF1502ASVL@PLCC44 [DX2044]
ATF1502ASVL@TQFP44 [DX3003]
ATF1504AS@PLCC68 [DX2068]
ATF1504AS@PQFP100 [DX3022]
ATF1504AS@TQFP44 [DX3003]
ATF1504ASL@PLCC68 [DX2068]
ATF1504ASL@PQFP100 [DX3022]
ATF1504ASL@TQFP44 [DX3003]
ATF1504ASV@PLCC68 [DX2068]
ATF1504ASV@PQFP100 [DX3022]
ATF1504ASV@TQFP44 [DX3003]
ATF1504ASVL@PLCC68 [DX2068]
ATF1504ASVL@PQFP100 [DX3022]
ATF1504ASVL@TQFP44 [DX3003]
ATF1508@PLCC84 [DX2084]
ATF1508@VQFP100 [DX3021]
ATF1508AS@PLCC84 [DX2084]
ATF1508AS@VQFP100 [DX3021]
ATF1508ASL@PLCC84 [DX2084]
ATF1508ASL@VQFP100 [DX3021]
ATF1508ASV@PLCC84 [DX2084]
ATF1508ASV@VQFP100 [DX3021]
ATF1508ASVL@PLCC84 [DX2084]
ATF1508ASVL@VQFP100 [DX3021]
ATF16LV8C@PLCC20 [DX2020]
ATF16LV8C@TSOP20 [DX1000]

ATF16LV8CEXT [DX0001]
ATF16LV8CEXT@PLCC20 [DX2020]
ATF16LV8CEXT@SOIC20 [DX1033]
ATF16LV8CEXT@TSOP20 [DX1000]
ATF16V8B [DX0001]
ATF16V8B@PLCC20 [DX2020]
ATF16V8B@SOIC20 [DX1033]
ATF16V8B@TSOP20 [DX1000]
ATF16V8BL [DX0001]
ATF16V8BL@PLCC20 [DX2020]
ATF16V8BL@SOIC20 [DX1033]
ATF16V8BL@TSOP20 [DX1000]
ATF16V8BQ [DX0001]
ATF16V8BQ@PLCC20 [DX2020]
ATF16V8BQ@SOIC20 [DX1033]
ATF16V8BQ@TSOP20 [DX1000]
ATF16V8BQL [DX0001]
ATF16V8BQL@PLCC20 [DX2020]
ATF16V8BQL@SOIC20 [DX1033]
ATF16V8BQL@TSOP20 [DX1000]
ATF16V8C [DX0001]
ATF16V8C@PLCC20 [DX2020]
ATF16V8C@SOIC20 [DX1033]
ATF16V8C@TSOP20 [DX1000]
ATF16V8CEXT [DX0001]
ATF16V8CEXT@PLCC20 [DX2020]
ATF16V8CEXT@SOIC20 [DX1033]
ATF16V8CEXT@TSOP20 [DX1000]
ATF16V8CZ [DX0001]
ATF16V8CZ@PLCC20 [DX2020]
ATF16V8CZ@SOIC20 [DX1033]
ATF16V8CZ@TSOP20 [DX1000]
ATF20V8B [DX0001]
ATF20V8B@PLCC28 [DX2028]
ATF20V8B@SOIC24 [DX1003]
ATF20V8BL [DX0001]
ATF20V8BL@PLCC28 [DX2028]
ATF20V8BL@SOIC24 [DX1003]
ATF20V8BQ [DX0001]
ATF20V8BQ@PLCC28 [DX2028]
ATF20V8BQ@SOIC24 [DX1003]
ATF20V8BQL [DX0001]
ATF20V8BQL@PLCC28 [DX2028]
ATF20V8BQL@SOIC24 [DX1003]
ATF22LV10C [DX0001]
ATF22LV10C(UES) [DX0001]
ATF22LV10C(UES)@PLCC28 [DX2028]
ATF22LV10C(UES)@SOIC24 [DX1033]
ATF22LV10C(UES)@TSSOP24 [DX1000]
ATF22LV10C@PLCC28 [DX2028]
ATF22LV10C@SOIC24 [DX1033]
ATF22LV10C@TSSOP24 [DX1000]
ATF22LV10CEXT [DX0001]
ATF22LV10CEXT@PLCC28 [DX2028]
ATF22LV10CEXT@SOIC24 [DX1033]
ATF22LV10CEXT@TSSOP24 [DX1000]
ATF22LV10CQZ [DX0001]
ATF22LV10CQZ(UES) [DX0001]
ATF22LV10CQZ(UES)@PLCC28 [DX2028]
ATF22LV10CQZ(UES)@SOIC24 [DX1033]
ATF22LV10CQZ(UES)@TSSOP24 [DX1000]
ATF22LV10CQZ@PLCC28 [DX2028]
ATF22LV10CQZ@SOIC24 [DX1033]
ATF22LV10CQZ@TSSOP24 [DX1000]
ATF22LV10CZ [DX0001]
ATF22LV10CZ(UES) [DX0001]
ATF22LV10CZ(UES)@PLCC28 [DX2028]
ATF22LV10CZ(UES)@SOIC24 [DX1033]
ATF22LV10CZ(UES)@TSSOP24 [DX1000]
ATF22LV10CZ@PLCC28 [DX2028]
ATF22LV10CZ@SOIC24 [DX1033]
ATF22LV10CZ@TSSOP24 [DX1000]
ATF22V10B [DX0001]
ATF22V10B@PLCC28 [DX2028]
ATF22V10B@SOIC24 [DX1033]
ATF22V10BL [DX0001]
ATF22V10BL@PLCC28 [DX2028]
ATF22V10BL@SOIC24 [DX1033]
ATF22V10BQ [DX0001]
ATF22V10BQ@PLCC28 [DX2028]
ATF22V10BQ@SOIC24 [DX1033]
ATF22V10BQL [DX0001]
ATF22V10BQL@PLCC28 [DX2028]
ATF22V10BQL@SOIC24 [DX1033]
ATF22V10C [DX0001]
ATF22V10C(UES) [DX0001]
ATF22V10C(UES)@PLCC28 [DX2028]
ATF22V10C(UES)@SOIC24 [DX1033]
ATF22V10C(UES)@TSSOP24 [DX1000]
ATF22V10C@PLCC28 [DX2028]
ATF22V10C@SOIC24 [DX1033]

ATF22V10C@TSSOP24 [DX1000]
ATF22V10CEXT [DX0001]
ATF22V10CEXT@PLCC28 [DX2028]
ATF22V10CEXT@SOIC24 [DX1033]
ATF22V10CEXT@TSSOP24 [DX1000]
ATF22V10CQ [DX0001]
ATF22V10CQ(UES) [DX0001]
ATF22V10CQ(UES)@PLCC28 [DX2028]
ATF22V10CQ(UES)@SOIC24 [DX1033]
ATF22V10CQ(UES)@TSSOP24 [DX1000]
ATF22V10CQ@PLCC28 [DX2028]
ATF22V10CQ@SOIC24 [DX1033]
ATF22V10CQ@TSSOP24 [DX1000]
ATF22V10CQZ [DX0001]
ATF22V10CQZ(UES) [DX0001]
ATF22V10CQZ(UES)@PLCC28 [DX2028]
ATF22V10CQZ(UES)@SOIC24 [DX1033]
ATF22V10CQZ(UES)@TSSOP24 [DX1000]
ATF22V10CQZ@PLCC28 [DX2028]
ATF22V10CQZ@SOIC24 [DX1033]
ATF22V10CQZ@TSSOP24 [DX1000]
ATF22V10CZ [DX0001]
ATF22V10CZ(UES) [DX0001]
ATF22V10CZ(UES)@PLCC28 [DX2028]
ATF22V10CZ(UES)@SOIC24 [DX1033]
ATF22V10CZ(UES)@TSSOP24 [DX1000]
ATF22V10CZ@PLCC28 [DX2028]
ATF22V10CZ@SOIC24 [DX1033]
ATF22V10CZ@TSSOP24 [DX1000]
ATF2500C(F2500C) [DX0001]
ATF2500C(F2500C)@PLCC44 [DX2044]
ATF2500C(F2500C)@TQFP44 [DX3003]
ATF2500C(V2500) [DX0001]
ATF2500C(V2500)@PLCC44 [DX2044]
ATF2500C(V2500)@TQFP44 [DX3003]
ATF2500C(V2500B) [DX0001]
ATF2500C(V2500B)@PLCC44 [DX2044]
ATF2500C(V2500B)@TQFP44 [DX3003]
ATF2500CL(F2500C) [DX0001]
ATF2500CL(F2500C)@PLCC44 [DX2044]
ATF2500CL(F2500C)@TQFP44 [DX3003]
ATF2500CL(V2500) [DX0001]
ATF2500CL(V2500)@PLCC44 [DX2044]
ATF2500CL(V2500)@TQFP44 [DX3003]
ATF2500CL(V2500B) [DX0001]
ATF2500CL(V2500B)@PLCC44 [DX2044]
ATF2500CL(V2500B)@TQFP44 [DX3003]
ATF2500CQ(F2500C) [DX0001]
ATF2500CQ(F2500C)@PLCC44 [DX2044]
ATF2500CQ(F2500C)@TQFP44 [DX3003]
ATF2500CQ(V2500B) [DX0001]
ATF2500CQ(V2500B)@PLCC44 [DX2044]
ATF2500CQ(V2500B)@TQFP44 [DX3003]
ATF2500CQL(F2500C) [DX0001]
ATF2500CQL(F2500C)@PLCC44 [DX2044]
ATF2500CQL(F2500C)@TQFP44 [DX3003]
ATF2500CQL(V2500B) [DX0001]
ATF2500CQL(V2500B)@PLCC44 [DX2044]
ATF2500CQL(V2500B)@TQFP44 [DX3003]
ATF750C(ATF750C mode) [DX0001]
ATF750C(ATV750 mode) [DX0001]
ATF750C(ATV750B mode) [DX0001]
ATF750C@PLCC28(ATF750C mode) [DX2028]
ATF750C@PLCC28(ATV750 mode) [DX2028]
ATF750C@PLCC28(ATV750B mode) [DX2028]
ATF750C@SOIC24(ATF750C mode) [DX1033]
ATF750C@SOIC24(ATV750 mode) [DX1033]
ATF750C@SOIC24(ATV750B mode) [DX1033]
ATF750CEXT(ATF750C mode) [DX0001]

ATF750CEXT@PLCC28(ATF750C mode) [DX2028]
ATF750CEXT@SOIC24(ATF750C mode) [DX1033]
ATF750CL(ATF750C mode) [DX0001] ATF750CL(ATV750 mode) [DX0001]
ATF750CL(ATV750B mode) [DX0001]
ATF750CL@PLCC28(ATF750C mode) [DX2028]
ATF750CL@PLCC28(ATV750 mode) [DX2028]
ATF750CL@PLCC28(ATV750B mode) [DX2028]
ATF750CL@SOIC24(ATF750C mode) [DX1033]
ATF750CL@SOIC24(ATV750 mode) [DX1033]
ATF750CL@SOIC24(ATV750B mode) [DX1033]
ATF750LVC(ATF750C mode) [DX0001] ATF750LVC(ATV750 mode) [DX0001]
ATF750LVC(ATV750B mode) [DX0001]
ATF750LVC@PLCC28(ATF750C mode) [DX2028]
ATF750LVC@PLCC28(ATV750 mode) [DX2028]
ATF750LVC@PLCC28(ATV750B mode) [DX2028]
ATF750LVC@SOIC24(ATF750C mode) [DX1033]
ATF750LVC@SOIC24(ATV750 mode) [DX1033]
ATF750LVC@SOIC24(ATV750B mode) [DX1033]
ATF750LVCEXT(ATF750C mode) [DX0001]
ATF750LVCEXT@PLCC28(ATF750Cmode) [DX2028]
ATF750LVCEXT@SOIC24(ATF750Cmode) [DX1033]
ATF750LVCL(ATF750C mode) [DX0001]
ATF750LVCL(ATV750 mode) [DX0001]
ATF750LVCL(ATV750B mode) [DX0001]
ATF750LVCL@PLCC28(ATF750C mode) [DX2028]
ATF750LVCL@PLCC28(ATV750 mode) [DX2028]
ATF750LVCL@PLCC28(ATV750B mode) [DX2028]
ATF750LVCL@SOIC24(ATF750C mode) [DX1033]
ATF750LVCL@SOIC24(ATV750 mode) [DX1033]
ATF750LVCL@SOIC24(ATV750B mode) [DX1033]
ATV22V10 [DX0001] ATV2500 [DX0001]
ATV2500@PLCC44 [DX2044] ATV2500B [DX0001]
ATV2500B@PLCC44 [DX2044] ATV2500BL [DX0001]
ATV2500BL@PLCC44 [DX2044] ATV2500BQ [DX0001]
ATV2500BQ@PLCC44 [DX2044] ATV2500BQL [DX0001]
ATV2500BQL@PLCC44 [DX2044] ATV2500H [DX0001]
ATV2500H@PLCC44 [DX2044] ATV2500L [DX0001]
ATV2500L@PLCC44 [DX2044] ATV750 [DX0001]
ATV750@PLCC28 [DX2028] ATV750@SOIC24 [DX1033]
ATV750B [DX0001] ATV750B@PLCC28 [DX2028]
ATV750B@SOIC24 [DX1033] ATV750BL [DX0001]
ATV750BL@PLCC28 [DX2028] ATV750BL@SOIC24 [DX1033]
ATV750L [DX0001] ATV750L@PLCC28 [DX2028]
ATV750L@SOIC24 [DX1033]

MICROCONTROLLER

AT32UC3A0128@TQFP144 [DX3035]
AT32UC3A0128@TQFP144(ISP) [DX0001]
AT32UC3A0256@TQFP144 [DX3035]
AT32UC3A0256@TQFP144(ISP) [DX0001]
AT32UC3A0512@TQFP144 [DX3035]
AT32UC3A0512@TQFP144(ISP) [DX0001]
AT32UC3A1128@TQFP100 [DX3021]
AT32UC3A1128@TQFP100(ISP) [DX0001]
AT32UC3A1256@TQFP100 [DX3021]
AT32UC3A1256@TQFP100(ISP) [DX0001]
AT32UC3A1512@TQFP100 [DX3021]
AT32UC3A1512@TQFP100(ISP) [DX0001]
AT32UC3A3128@FBGA144 [DX5128]
AT32UC3A3128@TQFP144 [DX3035]
AT32UC3A3128S@FBGA144 [DX5128]
AT32UC3A3128S@TQFP144 [DX3035]
AT32UC3A3256@FBGA144 [DX5128]
AT32UC3A3256@TQFP144 [DX3035]
AT32UC3A3256S@FBGA144 [DX5128]
AT32UC3A3256S@TQFP144 [DX3035]
AT32UC3A364@FBGA144 [DX5128]
AT32UC3A364@TQFP144 [DX3035]
AT32UC3A364S@FBGA144 [DX5128]
AT32UC3A364S@TQFP144 [DX3035]
AT32UC3A4128@FBGA144 [DX5215]
AT32UC3A4128S@FBGA144 [DX5215]
AT32UC3A4256@FBGA144 [DX5215]
AT32UC3A4256S@FBGA144 [DX5215]
AT32UC3A464@FBGA144 [DX5215]
AT32UC3A464S@FBGA144 [DX5215]
AT32UC3B0128@QFN64 [DX4023]
AT32UC3B0128@QFN64(ISP) [DX0001]
AT32UC3B0128@TQFP64 [DX3011]
AT32UC3B0128@TQFP64(ISP) [DX0001]
AT32UC3B0256@QFN64 [DX4023]
AT32UC3B0256@QFN64(ISP) [DX0001]
AT32UC3B0256@TQFP64 [DX3011]
AT32UC3B0256@TQFP64(ISP) [DX0001]
AT32UC3B0512@QFN64 [DX4023]
AT32UC3B0512@TQFP64 [DX3011]
AT32UC3B064@QFN64 [DX4023]
AT32UC3B064@QFN64(ISP) [DX0001]
AT32UC3B064@TQFP64 [DX3011]
AT32UC3B064@TQFP64(ISP) [DX0001]
AT32UC3B1128@QFN48 [DX4021]
AT32UC3B1128@QFN48(ISP) [DX0001]
AT32UC3B1128@TQFP48 [DX3007]
AT32UC3B1128@TQFP48(ISP) [DX0001]
AT32UC3B1256@QFN48 [DX4021]
AT32UC3B1256@QFN48(ISP) [DX0001]
AT32UC3B1256@TQFP48 [DX3007]
AT32UC3B1256@TQFP48(ISP) [DX0001]
AT32UC3B1512@QFN48 [DX4021]
AT32UC3B1512@TQFP48 [DX3007]
AT32UC3B164@QFN48 [DX4021]
AT32UC3B164@QFN48(ISP) [DX0001]
AT32UC3B164@TQFP48 [DX3007]
AT32UC3B164@TQFP48(ISP) [DX0001]
AT32UC3C0128C@LQFP144 [DX3035]
AT32UC3C0256C@LQFP144 [DX3035]
AT32UC3C0512C@LQFP144 [DX3035]
AT32UC3C064C@LQFP144 [DX3035]
AT32UC3C1128C@TQFP100 [DX3043]
AT32UC3C1256C@TQFP100 [DX3043]
AT32UC3C1512C@TQFP100 [DX3043]
AT32UC3C164C@TQFP100 [DX3043]
AT32UC3C2128C@QFN64 [DX4023]
AT32UC3C2128C@TQFP64 [DX3011]
AT32UC3C2256C@QFN64 [DX4023]
AT32UC3C2256C@TQFP64 [DX3011]
AT32UC3C2512C@QFN64 [DX4023]
AT32UC3C2512C@TQFP64 [DX3011]
AT32UC3C264C@QFN64 [DX4023]
AT32UC3C264C@TQFP64 [DX3011]
AT32UC3L0128@QFN48 [DX4021]
AT32UC3L0128@TQFP48 [DX3007]

AT32UC3L016@QFN48 [DX4021]
AT32UC3L0256@QFN48 [DX4021]
AT32UC3L032@QFN48 [DX4021]
AT32UC3L064@QFN48 [DX4021]
AT80F51 [DX0001]
AT80F51@TQFP44 [DX3003]
AT80F52@PLCC44 [DX2044]
AT87C51RB2 [DX0001]
AT87C51RB2@TQFP44 [DX3002]
AT87C51RC2@PLCC44 [DX2044]
AT87C51RD2 [DX0001]
AT87C51RD2@TQFP44 [DX3002]
AT87C51U2@PLCC44 [DX2044]
AT87C52X2 [DX0001]
AT87C52X2@TQFP44 [DX3002]
AT87C54X2@PLCC44 [DX2044]
AT87C58X2 [DX0001]
AT87C58X2@TQFP44 [DX3002]
AT87F51@PLCC44 [DX2044]
AT87F51RC [DX0001]
AT87F51RC@TQFP44 [DX3002]
AT87F52@PLCC44 [DX2044]
AT87F55 [DX0001]
AT87F55@TQFP44 [DX3002]
AT87F55WD@PLCC44 [DX2044]
AT87LV51 [DX0001]
AT87LV51@TQFP44 [DX3002]
AT87LV52@PLCC44 [DX2044]
AT89C1051 [DX0001]
AT89C1051U [DX0001]
AT89C2051 [DX0001]
AT89C2051X2 [DX0001]
AT89C4051 [DX0001]
AT89C51 [DX0001]
AT89C51@PQFP44 [DX3002]
AT89C5130A@PLCC52 [DX2052]
AT89C5130A@SOIC28 [DX1033]
AT89C5130AM@PLCC52 [DX2052]
AT89C5130AM@SOIC28 [DX1033]
AT89C5131@MLF48 [DX4021]
AT89C5131@SOIC28 [DX1033]
AT89C5131A@PLCC52 [DX2052]
AT89C5131A@SOIC28 [DX1033]
AT89C5131AL@PLCC52 [DX2052]
AT89C5131AL@SOIC28 [DX1033]
AT89C5131AM@PLCC52 [DX2052]
AT89C5131AM@SOIC28 [DX1033]
AT89C5132@TQFP80 [DX3018]
AT32UC3L016@TQFP48 [DX3007]
AT32UC3L0256@TQFP48 [DX3007]
AT32UC3L032@TQFP48 [DX3007]
AT32UC3L064@TQFP48 [DX3007]
AT80F51@PLCC44 [DX2044]
AT80F52 [DX0001]
AT80F52@TQFP44 [DX3003]
AT87C51RB2@PLCC44 [DX2044]
AT87C51RC2 [DX0001]
AT87C51RC2@TQFP44 [DX3002]
AT87C51RD2@PLCC44 [DX2044]
AT87C51U2 [DX0001]
AT87C51U2@TQFP44 [DX3002]
AT87C52X2@PLCC44 [DX2044]
AT87C54X2 [DX0001]
AT87C54X2@TQFP44 [DX3002]
AT87C58X2@PLCC44 [DX2044]
AT87F51 [DX0001]
AT87F51@TQFP44 [DX3002]
AT87F51RC@PLCC44 [DX2044]
AT87F52 [DX0001]
AT87F52@TQFP44 [DX3002]
AT87F55@PLCC44 [DX2044]
AT87F55WD [DX0001]
AT87F55WD@TQFP44 [DX3002]
AT87LV51@PLCC44 [DX2044]
AT87LV52 [DX0001]
AT87LV52@TQFP44 [DX3002]
AT89C1051@SOIC20 [DX1033]
AT89C1051U@SOIC20 [DX1033]
AT89C2051@SOIC20 [DX1033]
AT89C2051X2@SOIC20 [DX1033]
AT89C4051@SOIC20 [DX1033]
AT89C51@PLCC44 [DX2044]
AT89C51@TQFP44 [DX3003]
AT89C5130A@QFN32 [DX4016]
AT89C5130A@VQFP64 [DX3011]
AT89C5130AM@QFN32 [DX4016]
AT89C5130AM@VQFP64 [DX3011]
AT89C5131@PLCC52 [DX2052]
AT89C5131@VQFP64 [DX3011]
AT89C5131A@QFN32 [DX4016]
AT89C5131A@VQFP64 [DX3011]
AT89C5131AL@QFN32 [DX4016]
AT89C5131AL@VQFP64 [DX3011]
AT89C5131AM@QFN32 [DX4016]
AT89C5131AM@VQFP64 [DX3011]
AT89C51AC2@PLCC44 [DX2044]

AT89C51AC2@TQFP44 [DX3003]
AT89C51AC3@PLCC44 [DX2044]
AT89C51AC3@PLCC52 [DX2052]
AT89C51AC3@TQFP44 [DX3003]
AT89C51AC3@TQFP64 [DX3011]
AT89C51CC01@PLCC44 [DX2044]
AT89C51CC01@TQFP44 [DX3003]
AT89C51CC03C@PLCC44 [DX2044]
AT89C51CC03C@PLCC52 [DX2052]
AT89C51CC03C@TQFP44 [DX3003]
AT89C51CC03C@TQFP64 [DX3011]
AT89C51CC03CA@PLCC44 [DX2044]
AT89C51CC03CA@PLCC52 [DX2052]
AT89C51CC03CA@TQFP44 [DX3003]
AT89C51CC03CA@TQFP64 [DX3011]
AT89C51CC03U@PLCC44 [DX2044]
AT89C51CC03U@PLCC52 [DX2052]
AT89C51CC03U@TQFP44 [DX3003]
AT89C51CC03U@TQFP64 [DX3011]
AT89C51CC03UA@PLCC44 [DX2044]
AT89C51CC03UA@PLCC52 [DX2052]
AT89C51CC03UA@TQFP44 [DX3003]
AT89C51CC03UA@TQFP64 [DX3011]
AT89C51ED2 [DX0001]
AT89C51ED2@PLCC44 [DX2044]
AT89C51ED2@PLCC68 [DX2068]
AT89C51ED2@TQFP44 [DX3005]
AT89C51ED2@TQFP64 [DX3011]
AT89C51IC2@PLCC44 [DX2044]
AT89C51IC2@TQFP44 [DX3003]
AT89C51ID2 [DX0001]
AT89C51ID2@PLCC44 [DX2044]
AT89C51ID2@PLCC68 [DX2068]
AT89C51ID2@TQFP44 [DX3005]
AT89C51ID2@TQFP64 [DX3011]
AT89C51RB2 [DX0001]
AT89C51RB2@PLCC44 [DX2044]
AT89C51RB2@TQFP44 [DX3003]
AT89C51RC [DX0001]
AT89C51RC@PLCC44 [DX2044]
AT89C51RC@TQFP44 [DX3003]
AT89C51RC2 [DX0001]
AT89C51RC2@PLCC44 [DX2044]
AT89C51RC2@TQFP44 [DX3003]
AT89C51RD2 [DX0001]
AT89C51RD2@PLCC44 [DX2044]
AT89C51RD2@PLCC68 [DX2068]
AT89C51RD2@PLCC68(*) [SA648-B6808]
AT89C51RD2@TQFP44 [DX3005]
AT89C51RD2@TQFP64 [DX3011]
AT89C51RD2@TQFP64(*) [TA054-B006]
AT89C51RE2@PLCC44 [DX2044]
AT89C51RE2@VQFP44 [DX3005]
AT89C51RE2@VQFP64 [DX3011]
AT89C51SND1C@BGA81 [DX5071]
AT89C51SND1C@PLCC84 [DX2084]
AT89C51SND1C@TQFP80 [DX3018]
AT89C51SND2C@BGA100 [DX5055]
AT89C52 [DX0001]
AT89C52@PLCC44 [DX2044]
AT89C52@PQFP44 [DX3002]
AT89C52@TQFP44 [DX3003]
AT89C55 [DX0001]
AT89C55@PLCC44 [DX2044]
AT89C55@PQFP44 [DX3002]
AT89C55@TQFP44 [DX3003]
AT89C55WD [DX0001]
AT89C55WD@PLCC44 [DX2044]
AT89C55WD@TQFP44 [DX3003]
AT89LP2051 [DX0001]
AT89LP2051@SOIC20 [DX1033]
AT89LP2051@TSSOP20 [DX1000]
AT89LP2052 [DX0001]
AT89LP2052(ISP) [DX0001]
AT89LP2052@SOIC20 [DX1033]
AT89LP2052@SOIC20(ISP) [DX0001]
AT89LP2052@TSSOP20 [DX1000]
AT89LP2052@TSSOP20(ISP) [DX0001]
AT89LP213 [DX0001]
AT89LP213(ISP) [DX0001]
AT89LP213@TSSOP14 [DX1026]
AT89LP213@TSSOP14(ISP) [DX0001]
AT89LP214 [DX0001]
AT89LP214(ISP) [DX0001]
AT89LP214@TSSOP14 [DX1026]
AT89LP214@TSSOP14(ISP) [DX0001]
AT89LP216 [DX0001]
AT89LP216(ISP) [DX0001]
AT89LP216@SOIC16 [DX1033]
AT89LP216@SOIC16(ISP) [DX0001]
AT89LP216@TSSOP16 [DX1026]
AT89LP216@TSSOP16(ISP) [DX0001]
AT89LP3240 [DX0001]

AT89LP3240(ISP) [DX0001]
AT89LP3240@MLF44(ISP) [DX0001]
AT89LP3240@PLCC44(ISP) [DX0001]
AT89LP3240@TQFP44(ISP) [DX0001]
AT89LP4051@SOIC20 [DX1033]
AT89LP4052 [DX0001]
AT89LP4052@SOIC20 [DX1033]
AT89LP4052@TSSOP20 [DX1000]
AT89LP428 [DX0001]
AT89LP428@PLCC32 [DX2032]
AT89LP428@TQFP32 [DX3001]
AT89LP51 [DX0001]
AT89LP51@TQFP44 [DX3003]
AT89LP51ED2@MLF44 [DX4018]
AT89LP51ED2@TQFP44 [DX3003]
AT89LP51ID2(isp) [DX0001]
AT89LP51ID2@PLCC44 [DX2044]
AT89LP51RB2 [DX0001]
AT89LP51RB2@MLF44 [DX4018]
AT89LP51RB2@TQFP44 [DX3003]
AT89LP51RC2(isp) [DX0001]
AT89LP51RC2@PLCC44 [DX2044]
AT89LP51RD2 [DX0001]
AT89LP51RD2@MLF44 [DX4018]
AT89LP51RD2@TQFP44 [DX3003]
AT89LP52@PLCC44 [DX2044]
AT89LP6440 [DX0001]
AT89LP6440@MLF44 [DX4018]
AT89LP6440@PLCC44 [DX2044]
AT89LP6440@TQFP44 [DX3005]
AT89LP828 [DX0001]
AT89LP828@PLCC32 [DX2032]
AT89LP828@TQFP32 [DX3001]
AT89LS51 [DX0001]
AT89LS51@PLCC44 [DX2044]
AT89LS51@TQFP44 [DX3003]
AT89LS52 [DX0001]
AT89LS52@PLCC44 [DX2044]
AT89LS52@TQFP44 [DX3003]
AT89LS53 [DX0001]
AT89LS53@PLCC44 [DX2044]
AT89LS53@TQFP44 [DX3003]
AT89LS8252 [DX0001]
AT89LS8252@PLCC44 [DX2044]
AT89LS8252@TQFP44 [DX3003]
AT89LV51 [DX0001]
AT89LV51@TQFP44 [DX3003]
AT89LV52@PLCC44 [DX2044]
AT89LP3240@MLF44 [DX4018]
AT89LP3240@PLCC44 [DX2044]
AT89LP3240@TQFP44 [DX3005]
AT89LP4051 [DX0001]
AT89LP4051@TSSOP20 [DX1000]
AT89LP4052(ISP) [DX0001]
AT89LP4052@SOIC20(ISP) [DX0001]
AT89LP4052@TSSOP20(ISP) [DX0001]
AT89LP428(ISP) [DX0001]
AT89LP428@PLCC32(ISP) [DX0001]
AT89LP428@TQFP32(ISP) [DX0001]
AT89LP51@PLCC44 [DX2044]
AT89LP51ED2 [DX0001]
AT89LP51ED2@PLCC44 [DX2044]
AT89LP51ID2 [DX0001]
AT89LP51ID2@MLF44 [DX4018]
AT89LP51ID2@TQFP44 [DX3003]
AT89LP51RB2(isp) [DX0001]
AT89LP51RB2@PLCC44 [DX2044]
AT89LP51RC2 [DX0001]
AT89LP51RC2@MLF44 [DX4018]
AT89LP51RC2@TQFP44 [DX3003]
AT89LP51RD2(isp) [DX0001]
AT89LP51RD2@PLCC44 [DX2044]
AT89LP52 [DX0001]
AT89LP52@TQFP44 [DX3003]
AT89LP6440(ISP) [DX0001]
AT89LP6440@MLF44(ISP) [DX0001]
AT89LP6440@PLCC44(ISP) [DX0001]
AT89LP6440@TQFP44(ISP) [DX0001]
AT89LP828(ISP) [DX0001]
AT89LP828@PLCC32(ISP) [DX0001]
AT89LP828@TQFP32(ISP) [DX0001]
AT89LS51(ISP) [DX0001]
AT89LS51@PLCC44(ISP) [DX0001]
AT89LS51@TQFP44(ISP) [DX0001]
AT89LS52(ISP) [DX0001]
AT89LS52@PLCC44(ISP) [DX0001]
AT89LS52@TQFP44(ISP) [DX0001]
AT89LS53(ISP) [DX0001]
AT89LS53@PLCC44(ISP) [DX0001]
AT89LS53@TQFP44(ISP) [DX0001]
AT89LS8252(ISP) [DX0001]
AT89LS8252@PLCC44(ISP) [DX0001]
AT89LS8252@TQFP44(ISP) [DX0001]
AT89LV51@PLCC44 [DX2044]
AT89LV52 [DX0001]
AT89LV52@TQFP44 [DX3003]

AT89LV55 [DX0001]
AT89LV55@PLCC44 [DX2044]
AT89LV55@TQFP44 [DX3003]
AT89S2051 [DX0001]
AT89S2051@SOIC20 [DX1033]
AT89S4051 [DX0001]
AT89S4051@SOIC20 [DX1033]
AT89S51 [DX0001]
AT89S51(ISP) [DX0001]
AT89S51@PLCC44 [DX2044]
AT89S51@PLCC44(ISP) [DX0001]
AT89S51@TQFP44 [DX3003]
AT89S51@TQFP44(ISP) [DX0001]
AT89S52 [DX0001]
AT89S52(ISP) [DX0001]
AT89S52@PLCC44 [DX2044]
AT89S52@PLCC44(ISP) [DX0001]
AT89S52@TQFP44 [DX3003]
AT89S52@TQFP44(ISP) [DX0001]
AT89S53 [DX0001]
AT89S53(ISP) [DX0001]
AT89S53@PLCC44 [DX2044]
AT89S53@PLCC44(ISP) [DX0001]
AT89S53@TQFP44 [DX3003]
AT89S53@TQFP44(ISP) [DX0001]
AT89S54 [DX0001]
AT89S54@PLCC44 [DX2044]
AT89S54@TQFP44 [DX3003]
AT89S58 [DX0001]
AT89S58@PLCC44 [DX2044]
AT89S58@TQFP44 [DX3003]
AT89S64 [DX0001]
AT89S64@PLCC44 [DX2044]
AT89S64@TQFP44 [DX3005]
AT89S8252 [DX0001]
AT89S8252(ISP) [DX0001]
AT89S8252@PLCC44 [DX2044]
AT89S8252@PLCC44(ISP) [DX0001]
AT89S8252@PQFP44 [DX3002]
AT89S8252@TQFP44 [DX3003]
AT89S8252@TQFP44(ISP) [DX0001]
AT89S8253 [DX0001]
AT89S8253@PLCC44 [DX2044]
AT89S8253@TQFP44 [DX3003]
AT90CAN128@QFN64 [DX4023]
AT90CAN128@TQFP64 [DX3013]
AT90CAN32@QFN64 [DX4023]
AT90CAN32@TQFP64 [DX3013]
AT90CAN64@QFN64 [DX4023]
AT90CAN64@TQFP64 [DX3013]
AT90LS2323 [DX0001]
AT90LS2323@SOIC8 [DX1044]
AT90LS2333 [DX0001]
AT90LS2333@TQFP32 [DX3001]
AT90LS2343 [DX0001]
AT90LS2343@SOIC8 [DX1044]
AT90LS4433 [DX0001]
AT90LS4433@TQFP32 [DX3001]
AT90LS4434 [DX0001]
AT90LS4434@PLCC44 [DX2044]
AT90LS4434@TQFP44 [DX3003]
AT90LS8535 [DX0001]
AT90LS8535@PLCC44 [DX2044]
AT90LS8535@TQFP44 [DX3003]
AT90PWM1@SOIC24 [DX1033]
AT90PWM161@QFN32 [DX4015]
AT90PWM161@SOIC20 [DX1033]
AT90PWM2@SOIC24 [DX1033]
AT90PWM216@SOIC24 [DX1033]
AT90PWM2B@SOIC24 [DX1033]
AT90PWM3@QFN32 [DX4016]
AT90PWM3@SOIC32 [DX1069]
AT90PWM316@QFN32 [DX4016]
AT90PWM316@SOIC32 [DX1069]
AT90PWM3B@QFN32 [DX4016]
AT90PWM3B@SOIC32 [DX1069]
AT90PWM81@QFN32 [DX4030]
AT90PWM81@SOIC20 [DX1033]
AT90S1200 [DX0001]
AT90S1200@SOIC20 [DX1033]
AT90S1200@SSOP20 [DX1026]
AT90S1200A [DX0001]
AT90S1200A@SOIC20 [DX1033]
AT90S1200A@SSOP20 [DX1026]
AT90S2313 [DX0001]
AT90S2313@SOIC20 [DX1033]
AT90S2323 [DX0001]
AT90S2323@SOIC8 [DX1044]
AT90S2333 [DX0001]
AT90S2333@TQFP32 [DX3001]
AT90S2343 [DX0001]
AT90S2343@SOIC8 [DX1044]
AT90S4414 [DX0001]
AT90S4414@PLCC44 [DX2044]
AT90S4414@TQFP44 [DX3003]
AT90S4433 [DX0001]

AT90S4433@TQFP32 [DX3001]
AT90S4434 [DX0001]
AT90S4434@PLCC44 [DX2044]
AT90S4434@TQFP44 [DX3003]
AT90S8515 [DX0001]
AT90S8515@PLCC44 [DX2044]
AT90S8515@TQFP44 [DX3003]
AT90S8535 [DX0001]
AT90S8535@PLCC44 [DX2044]
AT90S8535@TQFP44 [DX3003]
AT90USB1286@QFN64 [DX4023]
AT90USB1286@TQFP64 [DX3013]
AT90USB1287@QFN64 [DX4023]
AT90USB1287@TQFP64 [DX3013]
AT90USB162@QFN32 [DX4015]
AT90USB162@QFN32(ISP) [DX0001]
AT90USB162@VQFP32 [DX3001]
AT90USB162@VQFP32(ISP) [DX0001]
AT90USB646@QFN64 [DX4023]
AT90USB646@TQFP64 [DX3013]
AT90USB647@QFN64 [DX4023]
AT90USB647@TQFP64 [DX3013]
AT90USB82@QFN32 [DX4015]
AT90USB82@QFN32(ISP) [DX0001]
AT91FR40162@FBGA121 [DX5126]
AT91FR40162S@FBGA121 [DX5126]
AT91FR4042@FBGA121 [DX5126]
AT91SAM7S128@LQFP64 [DX3011]
AT91SAM7S128@QFN64 [DX4023]
AT91SAM7S16@LQFP48 [DX3007]
AT91SAM7S16@QFN48 [DX4021]
AT91SAM7S161@LQFP64 [DX3011]
AT91SAM7S161@QFN64 [DX4023]
AT91SAM7S256@LQFP64 [DX3011]
AT91SAM7S256@QFN64 [DX4023]
AT91SAM7S32@LQFP48 [DX3007]
AT91SAM7S32@QFN48 [DX4021]
AT91SAM7S321@LQFP64 [DX3011]
AT91SAM7S321@QFN64 [DX4023]
AT91SAM7S512@LQFP64 [DX3011]
AT91SAM7S512@QFN64 [DX4023]
AT91SAM7S64@LQFP64 [DX3011]
AT91SAM7S64@QFN64 [DX4023]
AT91SAM7S64B@LQFP64 [DX3011]
AT91SAM7SE256AU@LQFP128 [DX3053]
AT91SAM7SE32AU@LQFP128 [DX3053]
AT91SAM7SE512AU@LQFP128 [DX3053]
AT91SAM7X128AU@LQFP100 [DX3021]
AT91SAM7X128CU@LFBGA100 [DX5055]
AT91SAM7X256AU@LQFP100 [DX3021]
AT91SAM7X256CU@LFBGA100 [DX5055]
AT91SAM7X512AU@LQFP100 [DX3021]
AT91SAM7X512CU@LFBGA100 [DX5055]
AT91SAM7XC128AU@LQFP100 [DX3021]
AT91SAM7XC128CU@LFBGA100 [DX5055]
AT91SAM7XC256AU@LQFP100 [DX3021]
AT91SAM7XC256CU@LFBGA100 [DX5055]
AT91SAM7XC512AU@LQFP100 [DX3021]
AT91SAM7XC512CU@LFBGA100 [DX5055]
ATA5780@VQFN32 [DX4015]
ATA5780N@VQFN32 [DX4015]
ATA5830@VQFN32 [DX4015]
ATA5830N@VQFN32 [DX4015]
ATC71RBX2 [DX0001]
ATC71RBX2@PLCC44 [DX2044]
ATC71RBX2@TQFP44 [DX3002]
ATC71RCX2 [DX0001]
ATC71RCX2@PLCC44 [DX2044]
ATC71RCX2@TQFP44 [DX3002]
ATC71RDX2 [DX0001]
ATC71RDX2@PLCC44 [DX2044]
ATC71RDX2@PLCC68 [DX2068]
ATC71RDX2@TQFP44 [DX3002]
ATC71RDX2@TQFP64 [DX3012]
ATC87C51 [DX0001]
ATC87C51@PLCC44 [DX2044]
ATC87C51@TQFP44 [DX3002]
ATC87C52 [DX0001]
ATC87C52@PLCC44 [DX2044]
ATC87C52@TQFP44 [DX3002]
ATC87C54 [DX0001]
ATC87C54@PLCC44 [DX2044]
ATC87C54@TQFP44 [DX3002]
ATC87C58 [DX0001]
ATC87C58@PLCC44 [DX2044]
ATC87C58@TQFP44 [DX3002]
ATMEGA103@TQFP64 [DX3013]
ATMEGA103L@TQFP64 [DX3013]
ATMEGA128@MLF64 [DX4023]
ATMEGA128@MLF64(ISP) [DX0001]
ATMEGA128@TQFP64 [DX3013]

ATMEGA128@TQFP64(ISP) [DX0001]
ATMEGA1280@CBGA100 [DX5055]
ATMEGA1280@CBGA100(ISP) [DX0001]
ATMEGA1280@TQFP100 [DX3043]
ATMEGA1280@TQFP100(ISP) [DX0001]
ATMEGA1280V@CBGA100 [DX5055]
ATMEGA1280V@CBGA100(ISP) [DX0001]
ATMEGA1280V@TQFP100 [DX3043]
ATMEGA1280V@TQFP100(ISP) [DX0001]
ATMEGA1281@MLF64 [DX4023]
ATMEGA1281@MLF64(ISP) [DX0001]
ATMEGA1281@TQFP64 [DX3013]
ATMEGA1281@TQFP64(ISP) [DX0001]
ATMEGA1281V@MLF64 [DX4023]
ATMEGA1281V@MLF64(ISP) [DX0001]
ATMEGA1281V@TQFP64 [DX3013]
ATMEGA1281V@TQFP64(ISP) [DX0001]
ATMEGA1284 [DX0001]
ATMEGA1284(ISP) [DX0001]
ATMEGA1284@MLF44 [DX4018]
ATMEGA1284@MLF44(ISP) [DX0001]
ATMEGA1284@TQFP44(ISP) [DX0001]
ATMEGA1284P [DX0001]
ATMEGA1284P(ISP) [DX0001]
ATMEGA1284P@MLF44 [DX4018]
ATMEGA1284P@MLF44(ISP) [DX0001]
ATMEGA1284P@TQFP44 [DX3003]
ATMEGA1284P@TQFP44(ISP) [DX0001]
ATMEGA1284PV [DX0001]
ATMEGA1284PV(ISP) [DX0001]
ATMEGA1284PV@MLF44 [DX4018]
ATMEGA1284PV@MLF44(ISP) [DX0001]
ATMEGA1284PV@TQFP44 [DX3003]
ATMEGA1284PV@TQFP44(ISP) [DX0001]
ATMEGA1284-Q44 [DX3003]
ATMEGA128A@MLF64 [DX4023]
ATMEGA128A@TQFP64 [DX3013]
ATMEGA128L@MLF64 [DX4023]
ATMEGA128L@MLF64(ISP) [DX0001]
ATMEGA128L@TQFP64 [DX3013]
ATMEGA128L@TQFP64(ISP) [DX0001]
ATMEGA128RFA1@MLF64 [DX4023]
ATMEGA128RFR2@QFN64 [DX4023]
ATMEGA16 [DX0001]
ATMEGA16@MLF44 [DX4018]
ATMEGA16@TQFP44 [DX3005]
ATMEGA161 [DX0001]
ATMEGA161@TQFP44 [DX3002]
ATMEGA161L [DX0001]
ATMEGA161L@TQFP44 [DX3002]
ATMEGA162 [DX0001]
ATMEGA162(ISP) [DX0001]
ATMEGA162@MLF44 [DX4018]
ATMEGA162@MLF44(ISP) [DX0001]
ATMEGA162@TQFP44 [DX3003]
ATMEGA162@TQFP44(ISP) [DX0001]
ATMEGA162V [DX0001]
ATMEGA162V(ISP) [DX0001]
ATMEGA162V@MLF44 [DX4018]
ATMEGA162V@MLF44(ISP) [DX0001]
ATMEGA162V@TQFP44 [DX3003]
ATMEGA162V@TQFP44(ISP) [DX0001]
ATMEGA163 [DX0001]
ATMEGA163@TQFP44 [DX3002]
ATMEGA163L [DX0001]
ATMEGA163L@TQFP44 [DX3002]
ATMEGA164 [DX0001]
ATMEGA164(ISP) [DX0001]
ATMEGA164@MLF44 [DX4018]
ATMEGA164@MLF44(ISP) [DX0001]
ATMEGA164@TQFP44 [DX3005]
ATMEGA164@TQFP44(ISP) [DX0001]
ATMEGA164A [DX0001]
ATMEGA164A(ISP) [DX0001]
ATMEGA164A@MLF44 [DX4018]
ATMEGA164A@MLF44(ISP) [DX0001]
ATMEGA164A@TQFP44 [DX3005]
ATMEGA164A@TQFP44(ISP) [DX0001]
ATMEGA164A@VFBGA49 [DX5154]
ATMEGA164A@VFBGA49(ISP) [DX0001]
ATMEGA164P [DX0001]
ATMEGA164P(ISP) [DX0001]
ATMEGA164P@MLF44 [DX4018]
ATMEGA164P@MLF44(ISP) [DX0001]
ATMEGA164P@TQFP44 [DX3005]
ATMEGA164P@TQFP44(ISP) [DX0001]
ATMEGA164PA [DX0001]
ATMEGA164PA(ISP) [DX0001]
ATMEGA164PA@MLF44 [DX4018]
ATMEGA164PA@MLF44(ISP) [DX0001]
ATMEGA164PA@TQFP44 [DX3005]
ATMEGA164PA@TQFP44(ISP) [DX0001]

ATMEGA164PA@VFBGA49 [DX5154]
ATMEGA164PA@VFBGA49(ISP) [DX0001]
ATMEGA164PV [DX0001]
ATMEGA164PV(ISP) [DX0001]
ATMEGA164PV@MLF44 [DX4018]
ATMEGA164PV@MLF44(ISP) [DX0001]
ATMEGA164PV@TQFP44 [DX3005]
ATMEGA164PV@TQFP44(ISP) [DX0001]
ATMEGA164V [DX0001]
ATMEGA164V(ISP) [DX0001]
ATMEGA164V@MLF44 [DX4018]
ATMEGA164V@MLF44(ISP) [DX0001]
ATMEGA164V@TQFP44 [DX3005]
ATMEGA164V@TQFP44(ISP) [DX0001]
ATMEGA165@MLF64 [DX4023]
ATMEGA165@TQFP64 [DX3013]
ATMEGA165A@MLF64 [DX4023]
ATMEGA165A@TQFP64 [DX3044]
ATMEGA165PA@MLF64 [DX4023]
ATMEGA165PA@TQFP64 [DX3044]
ATMEGA165V@MLF64 [DX4023]
ATMEGA165V@TQFP64 [DX3013]
ATMEGA168 [DX0001]
ATMEGA168(ISP) [DX0001]
ATMEGA168@MLF28 [DX4033]
ATMEGA168@MLF32 [DX4015]
ATMEGA168@MLP28(ISP) [DX0001]
ATMEGA168@MLP32(ISP) [DX0001]
ATMEGA168@TQFP32 [DX3001]
ATMEGA168@TQFP32(ISP) [DX0001]
ATMEGA168A [DX0001]
ATMEGA168A@MLF28 [DX4033]
ATMEGA168A@MLF32 [DX4015]
ATMEGA168A@TQFP32 [DX3001]
ATMEGA168P [DX0001]
ATMEGA168P(ISP) [DX0001]
ATMEGA168P@MLF28 [DX4033]
ATMEGA168P@MLF32 [DX4015]
ATMEGA168P@MLP28(ISP) [DX0001]
ATMEGA168P@MLP32(ISP) [DX0001]
ATMEGA168P@TQFP32 [DX3001]
ATMEGA168P@TQFP32(ISP) [DX0001]
ATMEGA168PA [DX0001]
ATMEGA168PA@MLF28 [DX4033]
ATMEGA168PA@MLF32 [DX4015]
ATMEGA168PA@TQFP32 [DX3001]
ATMEGA168PV [DX0001]
ATMEGA168PV(ISP) [DX0001]
ATMEGA168PV@MLF28 [DX4033]
ATMEGA168PV@MLF32 [DX4015]
ATMEGA168PV@MLP28(ISP) [DX0001]
ATMEGA168PV@MLP32(ISP) [DX0001]
ATMEGA168PV@TQFP32 [DX3001]
ATMEGA168PV@TQFP32(ISP) [DX0001]
ATMEGA168V [DX0001]
ATMEGA168V(ISP) [DX0001]
ATMEGA168V@MLF28 [DX4033]
ATMEGA168V@MLF32 [DX4015]
ATMEGA168V@MLP28(ISP) [DX0001]
ATMEGA168V@MLP32(ISP) [DX0001]
ATMEGA168V@TQFP32 [DX3001]
ATMEGA168V@TQFP32(ISP) [DX0001]
ATMEGA169@MLF64 [DX4023]
ATMEGA169@MLF64(ISP) [DX0001]
ATMEGA169@TQFP64 [DX3013]
ATMEGA169@TQFP64(ISP) [DX0001]
ATMEGA169A@MLF64 [DX4023]
ATMEGA169A@TQFP64 [DX3013]
ATMEGA169P@MLF64 [DX4023]
ATMEGA169P@MLF64(ISP) [DX0001]
ATMEGA169P@TQFP64 [DX3013]
ATMEGA169P@TQFP64(ISP) [DX0001]
ATMEGA169PA@MLF64 [DX4023]
ATMEGA169PA@TQFP64 [DX3013]
ATMEGA169PV@MLF64 [DX4023]
ATMEGA169PV@MLF64(ISP) [DX0001]
ATMEGA169PV@TQFP64 [DX3013]
ATMEGA169PV@TQFP64(ISP) [DX0001]
ATMEGA169V@MLF64 [DX4023]
ATMEGA169V@MLF64(ISP) [DX0001]
ATMEGA169V@TQFP64 [DX3013]
ATMEGA169V@TQFP64(ISP) [DX0001]
ATMEGA16A [DX0001]
ATMEGA16A@MLF44 [DX4018]
ATMEGA16A@TQFP44 [DX3005]
ATMEGA16HVA@TSOP28 [DX1024]
ATMEGA16HVA@TSOP28(ISP) [DX0001]
ATMEGA16HVB@TSSOP44 [DX1012]
ATMEGA16L [DX0001]
ATMEGA16L@MLF44 [DX4018]
ATMEGA16L@TQFP44 [DX3005]
ATMEGA16M1@MLF32 [DX4015]
ATMEGA16M1@MLF32(ISP) [DX0001]
ATMEGA16M1@TQFP32 [DX3001]

ATMEGA16M1@TQFP32(ISP) [DX0001]
ATMEGA16U2@MLF32 [DX4015]
ATMEGA16U2@VQFP32 [DX3001]
ATMEGA16U4@MLF44 [DX4018]
ATMEGA16U4@MLF44(ISP) [DX0001]
ATMEGA16U4@TQFP44 [DX3003]
ATMEGA16U4@TQFP44(ISP) [DX0001]
ATMEGA2560@CBGA100 [DX5055]
ATMEGA2560@CBGA100(ISP) [DX0001]
ATMEGA2560@TQFP100 [DX3043]
ATMEGA2560@TQFP100(ISP) [DX0001]
ATMEGA2560V@CBGA100 [DX5055]
ATMEGA2560V@CBGA100(ISP) [DX0001]
ATMEGA2560V@TQFP100 [DX3043]
ATMEGA2560V@TQFP100(ISP) [DX0001]
ATMEGA2561@MLF64 [DX4023]
ATMEGA2561@MLF64(ISP) [DX0001]
ATMEGA2561@TQFP64 [DX3013]
ATMEGA2561@TQFP64(ISP) [DX0001]
ATMEGA2561V@MLF64 [DX4023]
ATMEGA2561V@MLF64(ISP) [DX0001]
ATMEGA2561V@TQFP64 [DX3013]
ATMEGA2561V@TQFP64(ISP) [DX0001]
ATMEGA256RFR2@QFN64 [DX4023]
ATMEGA32 [DX0001]
ATMEGA32@MLF44 [DX4018]
ATMEGA32@TQFP44 [DX3005]
ATMEGA323 [DX0001]
ATMEGA323@TQFP44 [DX3002]
ATMEGA323L [DX0001]
ATMEGA323L@TQFP44 [DX3002]
ATMEGA324 [DX0001]
ATMEGA324(ISP) [DX0001]
ATMEGA324@MLF44 [DX4018]
ATMEGA324@MLF44(ISP) [DX0001]
ATMEGA324@TQFP44 [DX3005]
ATMEGA324@TQFP44(ISP) [DX0001]
ATMEGA324A [DX0001]
ATMEGA324A(ISP) [DX0001]
ATMEGA324A@MLF44 [DX4018]
ATMEGA324A@MLF44(ISP) [DX0001]
ATMEGA324A@TQFP44 [DX3005]
ATMEGA324A@TQFP44(ISP) [DX0001]
ATMEGA324A@VFBGA49 [DX5154]
ATMEGA324A@VFBGA49(ISP) [DX0001]
ATMEGA324P [DX0001]
ATMEGA324P(ISP) [DX0001]
ATMEGA324P@MLF44 [DX4018]
ATMEGA324P@MLF44(ISP) [DX0001]
ATMEGA324P@TQFP44 [DX3005]
ATMEGA324P@TQFP44(ISP) [DX0001]
ATMEGA324PA [DX0001]
ATMEGA324PA(ISP) [DX0001]
ATMEGA324PA@MLF44 [DX4018]
ATMEGA324PA@MLF44(ISP) [DX0001]
ATMEGA324PA@TQFP44 [DX3005]
ATMEGA324PA@TQFP44(ISP) [DX0001]
ATMEGA324PA@VFBGA49 [DX5154]
ATMEGA324PA@VFBGA49(ISP) [DX0001]
ATMEGA324PV [DX0001]
ATMEGA324PV(ISP) [DX0001]
ATMEGA324PV@MLF44 [DX4018]
ATMEGA324PV@MLF44(ISP) [DX0001]
ATMEGA324PV@TQFP44 [DX3005]
ATMEGA324PV@TQFP44(ISP) [DX0001]
ATMEGA324V [DX0001]
ATMEGA324V(ISP) [DX0001]
ATMEGA324V@MLF44 [DX4018]
ATMEGA324V@MLF44(ISP) [DX0001]
ATMEGA324V@TQFP44 [DX3005]
ATMEGA324V@TQFP44(ISP) [DX0001]
ATMEGA325@MLF64 [DX4023]
ATMEGA325@TQFP64 [DX3013]
ATMEGA3250@TQFP100 [DX3043]
ATMEGA3250P@TQFP100 [DX3043]
ATMEGA3250PV@TQFP100 [DX3043]
ATMEGA3250V@TQFP100 [DX3043]
ATMEGA325P@MLF64 [DX4023]
ATMEGA325P@TQFP64 [DX3013]
ATMEGA325PV@MLF64 [DX4023]
ATMEGA325PV@TQFP64 [DX3013]
ATMEGA325V@MLF64 [DX4023]
ATMEGA325V@TQFP64 [DX3013]
ATMEGA328 [DX0001]
ATMEGA328@MLF28 [DX4033]
ATMEGA328@MLF32 [DX4015]
ATMEGA328@TQFP32 [DX3001]
ATMEGA328P [DX0001]
ATMEGA328P(ISP) [DX0001]
ATMEGA328P@MLF28 [DX4033]
ATMEGA328P@MLF32 [DX4015]

ATMEGA328P@MLP28(ISP) [DX0001]
ATMEGA328P@MLP32(ISP) [DX0001]
ATMEGA328P@TQFP32 [DX3001]
ATMEGA328P@TQFP32(ISP) [DX0001]
ATMEGA328PB@TQFP32 [DX3001]
ATMEGA328PV [DX0001]
ATMEGA328PV(ISP) [DX0001]
ATMEGA328PV@MLF28 [DX4033]
ATMEGA328PV@MLF32 [DX4015]
ATMEGA328PV@MLP28(ISP) [DX0001]
ATMEGA328PV@MLP32(ISP) [DX0001]
ATMEGA328PV@TQFP32 [DX3001]
ATMEGA328PV@TQFP32(ISP) [DX0001]
ATMEGA329@MLF64 [DX4023]
ATMEGA329@TQFP64 [DX3013]
ATMEGA3290@TQFP100 [DX3043]
ATMEGA3290P@TQFP100 [DX3043]
ATMEGA3290PV@TQFP100 [DX3043]
ATMEGA3290V@TQFP100 [DX3043]
ATMEGA329P@MLF64 [DX4023]
ATMEGA329P@TQFP64 [DX3013]
ATMEGA329PV@MLF64 [DX4023]
ATMEGA329PV@TQFP64 [DX3013]
ATMEGA329V@MLF64 [DX4023]
ATMEGA329V@TQFP64 [DX3013]
ATMEGA32A [DX0001]
ATMEGA32A@MLF44 [DX4018]
ATMEGA32A@TQFP44 [DX3005]
ATMEGA32C1@MLF32 [DX4015]
ATMEGA32C1@MLF32(ISP) [DX0001]
ATMEGA32C1@TQFP32 [DX3001]
ATMEGA32C1@TQFP32(ISP) [DX0001]
ATMEGA32HVB@TSSOP44 [DX1012]
ATMEGA32L [DX0001]
ATMEGA32L@MLF44 [DX4018]
ATMEGA32L@TQFP44 [DX3005]
ATMEGA32M1@MLF32 [DX4015]
ATMEGA32M1@MLF32(ISP) [DX0001]
ATMEGA32M1@TQFP32 [DX3001]
ATMEGA32M1@TQFP32(ISP) [DX0001]
ATMEGA32U2@MLF32 [DX4015]
ATMEGA32U2@VQFP32 [DX3001]
ATMEGA32U4@MLF44 [DX4018]
ATMEGA32U4@MLF44(ISP) [DX0001]
ATMEGA32U4@TQFP44 [DX3003]
ATMEGA32U4@TQFP44(ISP) [DX0001]
ATMEGA406@LQFP48 [DX3007]
ATMEGA48 [DX0001]
ATMEGA48(ISP) [DX0001]
ATMEGA48@MLF28 [DX4033]
ATMEGA48@MLF32 [DX4015]
ATMEGA48@MLP28(ISP) [DX0001]
ATMEGA48@MLP32(ISP) [DX0001]
ATMEGA48@TQFP32 [DX3001]
ATMEGA48@TQFP32(ISP) [DX0001]
ATMEGA48A [DX0001]
ATMEGA48A@MLF28 [DX4033]
ATMEGA48A@MLF32 [DX4015]
ATMEGA48A@TQFP32 [DX3001]
ATMEGA48P [DX0001]
ATMEGA48P(ISP) [DX0001]
ATMEGA48P@MLF28 [DX4033]
ATMEGA48P@MLF32 [DX4015]
ATMEGA48P@MLP28(ISP) [DX0001]
ATMEGA48P@MLP32(ISP) [DX0001]
ATMEGA48P@TQFP32 [DX3001]
ATMEGA48P@TQFP32(ISP) [DX0001]
ATMEGA48PA [DX0001]
ATMEGA48PA@MLF28 [DX4033]
ATMEGA48PA@MLF32 [DX4015]
ATMEGA48PA@TQFP32 [DX3001]
ATMEGA48PV [DX0001]
ATMEGA48PV(ISP) [DX0001]
ATMEGA48PV@MLF28 [DX4033]
ATMEGA48PV@MLF32 [DX4015]
ATMEGA48PV@MLP28(ISP) [DX0001]
ATMEGA48PV@MLP32(ISP) [DX0001]
ATMEGA48PV@TQFP32 [DX3001]
ATMEGA48PV@TQFP32(ISP) [DX0001]
ATMEGA48V [DX0001]
ATMEGA48V(ISP) [DX0001]
ATMEGA48V@MLF28 [DX4033]
ATMEGA48V@MLF32 [DX4015]
ATMEGA48V@MLP28(ISP) [DX0001]
ATMEGA48V@MLP32(ISP) [DX0001]
ATMEGA48V@TQFP32 [DX3001]
ATMEGA48V@TQFP32(ISP) [DX0001]
ATMEGA603@TQFP64 [DX3013]
ATMEGA603L@TQFP64 [DX3013]
ATMEGA64@MLF64 [DX4023]
ATMEGA64@MLF64(ISP) [DX0001]
ATMEGA64@TQFP64 [DX3013]
ATMEGA64@TQFP64(ISP) [DX0001]
ATMEGA640@CBGA100 [DX5055]
ATMEGA640@CBGA100(ISP) [DX0001]
ATMEGA640@TQFP100 [DX3043]

ATMEGA640@TQFP100(ISP) [DX0001]
ATMEGA640V@CBGA100(ISP) [DX0001]
ATMEGA640V@TQFP100(ISP) [DX0001]
ATMEGA644(ISP) [DX0001]
ATMEGA644@MLF44(ISP) [DX0001]
ATMEGA644@TQFP44(ISP) [DX0001]
ATMEGA644A(ISP) [DX0001]
ATMEGA644A@MLF44(ISP) [DX0001]
ATMEGA644A@TQFP44(ISP) [DX0001]
ATMEGA644P(ISP) [DX0001]
ATMEGA644P@MLF44(ISP) [DX0001]
ATMEGA644P@TQFP44(ISP) [DX0001]
ATMEGA644PA(ISP) [DX0001]
ATMEGA644PA@MLF44(ISP) [DX0001]
ATMEGA644PA@TQFP44(ISP) [DX0001]
ATMEGA644PV(ISP) [DX0001]
ATMEGA644PV@MLF44(ISP) [DX0001]
ATMEGA644PV@TQFP44(ISP) [DX0001]
ATMEGA644V(ISP) [DX0001]
ATMEGA644V@MLF44(ISP) [DX0001]
ATMEGA644V@TQFP44(ISP) [DX0001]
ATMEGA645@TQFP64 [DX3013]
ATMEGA6450V@TQFP100 [DX3043]
ATMEGA645V@TQFP64 [DX3013]
ATMEGA649@TQFP64 [DX3013]
ATMEGA6490V@TQFP100 [DX3043]
ATMEGA649V@TQFP64 [DX3013]
ATMEGA64A@TQFP64 [DX3013]
ATMEGA64C1@MLF32(ISP) [DX0001]
ATMEGA64C1@TQFP32(ISP) [DX0001]
ATMEGA64L@MLF64(ISP) [DX0001]
ATMEGA64L@TQFP64(ISP) [DX0001]
ATMEGA64M1@MLF32(ISP) [DX0001]
ATMEGA64M1@TQFP32(ISP) [DX0001]
ATMEGA8 [DX0001]
ATMEGA8@MLF32 [DX4015]
ATMEGA8@TQFP32 [DX3001]
ATMEGA8515 [DX0001]
ATMEGA8515@PLCC44 [DX2044]
ATMEGA8515L [DX0001]
ATMEGA8515L@PLCC44 [DX2044]
ATMEGA8535 [DX0001]
ATMEGA8535@MLF44 [DX4018]
ATMEGA8535@PLCC44 [DX2044]
ATMEGA8535@TQFP44 [DX3005]
ATMEGA8535L [DX0001]
ATMEGA8535L@MLF44 [DX4018]
ATMEGA8535L@PLCC44 [DX2044]
ATMEGA640V@CBGA100 [DX5055]
ATMEGA640V@TQFP100 [DX3043]
ATMEGA644 [DX0001]
ATMEGA644@MLF44 [DX4018]
ATMEGA644@TQFP44 [DX3005]
ATMEGA644A [DX0001]
ATMEGA644A@MLF44 [DX4018]
ATMEGA644A@TQFP44 [DX3005]
ATMEGA644P [DX0001]
ATMEGA644P@MLF44 [DX4018]
ATMEGA644P@TQFP44 [DX3005]
ATMEGA644PA [DX0001]
ATMEGA644PA@MLF44 [DX4018]
ATMEGA644PA@TQFP44 [DX3005]
ATMEGA644PV [DX0001]
ATMEGA644PV@MLF44 [DX4018]
ATMEGA644PV@TQFP44 [DX3005]
ATMEGA644V [DX0001]
ATMEGA644V@MLF44 [DX4018]
ATMEGA644V@TQFP44 [DX3005]
ATMEGA645@MLF64 [DX4023]
ATMEGA6450@TQFP100 [DX3043]
ATMEGA645V@MLF64 [DX4023]
ATMEGA649@MLF64 [DX4023]
ATMEGA6490@TQFP100 [DX3043]
ATMEGA649V@MLF64 [DX4023]
ATMEGA64A@MLF64 [DX4023]
ATMEGA64C1@MLF32 [DX4015]
ATMEGA64C1@TQFP32 [DX3001]
ATMEGA64L@MLF64 [DX4023]
ATMEGA64L@TQFP64 [DX3013]
ATMEGA64M1@MLF32 [DX4015]
ATMEGA64M1@TQFP32 [DX3001]
ATMEGA64RFR2@QFN64 [DX4023]
ATMEGA8(ISP) [DX0001]
ATMEGA8@MLF32(ISP) [DX0001]
ATMEGA8@TQFP32(ISP) [DX0001]
ATMEGA8515@MLF44 [DX4018]
ATMEGA8515@TQFP44 [DX3005]
ATMEGA8515L@MLF44 [DX4018]
ATMEGA8515L@TQFP44 [DX3005]
ATMEGA8535(ISP) [DX0001]
ATMEGA8535@MLF44(ISP) [DX0001]
ATMEGA8535@PLCC44(ISP) [DX0001]
ATMEGA8535@TQFP44(ISP) [DX0001]
ATMEGA8535L(ISP) [DX0001]
ATMEGA8535L@MLF44(ISP) [DX0001]
ATMEGA8535L@PLCC44(ISP) [DX0001]

ATMEGA8535L@TQFP44 [DX3005]
ATMEGA88 [DX0001]
ATMEGA88@MLF28 [DX4033]
ATMEGA88@MLP28(ISP) [DX0001]
ATMEGA88@TQFP32 [DX3001]
ATMEGA88A [DX0001]
ATMEGA88A@MLF32 [DX4015]
ATMEGA88P [DX0001]
ATMEGA88P@MLF28 [DX4033]
ATMEGA88P@MLP28(ISP) [DX0001]
ATMEGA88P@TQFP32 [DX3001]
ATMEGA88PA [DX0001]
ATMEGA88PA@MLF32 [DX4015]
ATMEGA88PV [DX0001]
ATMEGA88PV@MLF28 [DX4033]
ATMEGA88PV@MLP28(ISP) [DX0001]
ATMEGA88PV@TQFP32 [DX3001]
ATMEGA88V [DX0001]
ATMEGA88V@MLF28 [DX4033]
ATMEGA88V@MLP28(ISP) [DX0001]
ATMEGA88V@TQFP32 [DX3001]
ATMEGA8A [DX0001]
ATMEGA8A@TQFP32 [DX3001]
ATMEGA8HVA@TSOP28(ISP) [DX0001]
ATMEGA8L(ISP) [DX0001]
ATMEGA8L@MLF32(ISP) [DX0001]
ATMEGA8L@TQFP32(ISP) [DX0001]
ATMEGA8U2@VQFP32 [DX3001]
ATSAM3N00A@QFN48 [DX4021]
ATSAM3N00B@QFN64 [DX4023]
ATSAM3N0A@QFN48 [DX4021]
ATSAM3N0B@QFN64 [DX4023]
ATSAM3N0C@LQFP100 [DX3043]
ATSAM3N1A@QFN48 [DX4021]
ATSAM3N1B@QFN64 [DX4023]
ATSAM3N1C@LQFP100 [DX3043]
ATSAM3N2A@QFN48 [DX4021]
ATSAM3N2B@QFN64 [DX4023]
ATSAM3N2C@LQFP100 [DX3043]
ATSAM3N4A@QFN48 [DX4021]
ATSAM3N4B@QFN64 [DX4023]
ATSAM3N4C@LQFP100 [DX3043]
ATSAM3S1A@QFN48 [DX4021]
ATSAM3S1B@QFN64 [DX4023]
ATSAM3S1C@LQFP100 [DX3043]
ATSAM3S2A@QFN48 [DX4021]
ATSAM3S2B@QFN64 [DX4023]
ATSAM3S2C@LQFP100 [DX3043]
ATMEGA8535L@TQFP44(ISP) [DX0001]
ATMEGA88(ISP) [DX0001]
ATMEGA88@MLF32 [DX4015]
ATMEGA88@MLP32(ISP) [DX0001]
ATMEGA88@TQFP32(ISP) [DX0001]
ATMEGA88A@MLF28 [DX4033]
ATMEGA88A@TQFP32 [DX3001]
ATMEGA88P(ISP) [DX0001]
ATMEGA88P@MLF32 [DX4015]
ATMEGA88P@MLP32(ISP) [DX0001]
ATMEGA88P@TQFP32(ISP) [DX0001]
ATMEGA88PA@MLF28 [DX4033]
ATMEGA88PA@TQFP32 [DX3001]
ATMEGA88PV(ISP) [DX0001]
ATMEGA88PV@MLF32 [DX4015]
ATMEGA88PV@MLP32(ISP) [DX0001]
ATMEGA88PV@TQFP32(ISP) [DX0001]
ATMEGA88V(ISP) [DX0001]
ATMEGA88V@MLF32 [DX4015]
ATMEGA88V@MLP32(ISP) [DX0001]
ATMEGA88V@TQFP32(ISP) [DX0001]
ATMEGA8A@MLF32 [DX4015]
ATMEGA8HVA@TSOP28 [DX1024]
ATMEGA8L [DX0001]
ATMEGA8L@MLF32 [DX4015]
ATMEGA8L@TQFP32 [DX3001]
ATMEGA8U2@MLF32 [DX4015]
ATSAM3N00A@LQFP48 [DX3007]
ATSAM3N00B@LQFP64 [DX3011]
ATSAM3N0A@LQFP48 [DX3007]
ATSAM3N0B@LQFP64 [DX3011]
ATSAM3N0C@BGA100 [DX5055]
ATSAM3N1A@LQFP48 [DX3007]
ATSAM3N1B@LQFP64 [DX3011]
ATSAM3N1C@BGA100 [DX5055]
ATSAM3N2A@LQFP48 [DX3007]
ATSAM3N2B@LQFP64 [DX3011]
ATSAM3N2C@BGA100 [DX5055]
ATSAM3N4A@LQFP48 [DX3007]
ATSAM3N4B@LQFP64 [DX3011]
ATSAM3N4C@BGA100 [DX5055]
ATSAM3S1A@LQFP48 [DX3007]
ATSAM3S1B@LQFP64 [DX3011]
ATSAM3S1C@BGA100 [DX5055]
ATSAM3S2A@LQFP48 [DX3007]
ATSAM3S2B@LQFP64 [DX3011]
ATSAM3S2C@BGA100 [DX5055]
ATSAM3S4A@LQFP48 [DX3007]

ATSAM3S4A@QFN48 [DX4021]
ATSAM3S4B@QFN64 [DX4023]
ATSAM3S4B@QFP64 [DX3011]
ATSAM3S4C@BGA100 [DX5055]
ATSAM3S4C@QFP100 [DX3043]
ATSAM3S8B@LQFP64 [DX3011]
ATSAM3S8B@QFN64 [DX4023]
ATSAM3S8C@LQFP100 [DX3043]
ATSAM3S8C@TBGA100 [DX5055]
ATSAM3SD8B@LQFP64 [DX3011]
ATSAM3SD8B@QFN64 [DX4023]
ATSAM3SD8C@LQFP100 [DX3043]
ATSAM3SD8C@TBGA100 [DX5055]
ATSAM3U1C@FBGA100 [DX5055]
ATSAM3U1C@LQFP100 [DX3043]
ATSAM3U1E@FBGA144 [DX5107]
ATSAM3U1E@LQFP144 [DX3051]
ATSAM3U2C@FBGA100 [DX5055]
ATSAM3U2C@LQFP100 [DX3043]
ATSAM3U2E@FBGA144 [DX5107]
ATSAM3U2E@LQFP144 [DX3051]
ATSAM3U4C@FBGA100 [DX5055]
ATSAM3U4C@LQFP100 [DX3043]
ATSAM3U4E@FBGA144 [DX5107]
ATSAM3U4E@LQFP144 [DX3051]
ATSAM3X4C@LQFP100 [DX3043]
ATSAM3X4C@LQFP100(swd) [DX3021]
ATSAM3X8C@LQFP100 [DX3043]
ATSAM3X8E@LQFP144 [DX3051]
ATSAM4CMS32CA-AU@TQFP100 [DX3021]
ATSAM4CMS4CB-AU@TQFP100 [DX3021]
ATSAM4CMS8CB-AU@TQFP100 [DX3021]
ATSAM4E16C@LQFP100 [DX3043]
ATSAM4E16C@TFBGA100 [DX5055]
ATSAM4E16E@LFBGA144 [DX5107]
ATSAM4E16E@LQFP144 [DX3051]
ATSAM4E8C@LQFP100 [DX3043]
ATSAM4E8C@TFBGA100 [DX5055]
ATSAM4E8E@LFBGA144 [DX5107]
ATSAM4E8E@LQFP144 [DX3051]
ATSAM4N16B@LQFP64 [DX3011]
ATSAM4N16B@QFN64 [DX4023]
ATSAM4N16C@LQFP100 [DX3043]
ATSAM4N16C@TFBGA100 [DX5055]
ATSAM4N16C@VFBGA100 [DX5215]
ATSAM4N8A@LQFP48 [DX3007]
ATSAM4N8A@QFN48 [DX4021]
ATSAM4N8B@LQFP64 [DX3011]
ATSAM4N8B@QFN64 [DX4023]
ATSAM4N8C@LQFP100 [DX3043]
ATSAM4N8C@TFBGA100 [DX5055]
ATSAM4N8C@VFBGA100 [DX5215]
ATSAM4S16B@LQFP64 [DX3011]
ATSAM4S16B@QFN64 [DX4023]
ATSAM4S16C@LQFP100 [DX3043]
ATSAM4S16C@TFBGA100 [DX5055]
ATSAM4S16C@VFBGA100 [DX5215]
ATSAM4S4B@LQFP64 [DX3011]
ATSAM4S4B@QFN64 [DX4023]
ATSAM4S8B@LQFP64 [DX3011]
ATSAM4S8B@QFN64 [DX4023]
ATSAM4S8C@LQFP100 [DX3043]
ATSAM4S8C@TFBGA100 [DX5055]
ATSAM4S8C@VFBGA100 [DX5215]
ATSAM4SD16B@LQFP64 [DX3011]
ATSAM4SD16B@QFN64 [DX4023]
ATSAM4SD16C@LQFP100 [DX3043]
ATSAM4SD16C@TFBGA100 [DX5055]
ATSAM4SD16C@VFBGA100 [DX5215]
ATSAM4SD32B@LQFP64 [DX3011]
ATSAM4SD32B@QFN64 [DX4023]
ATSAM4SD32C@LQFP100 [DX3043]
ATSAM4SD32C@TFBGA100 [DX5055]
ATSAM4SD32C@VFBGA100 [DX5215]
ATSAMD10C13A@SOP14 [DX1016]
ATSAMD10C14A@SOP14 [DX1016]
ATSAMD10D13A@QFN24 [DX4012]
ATSAMD10D13A@SOP20 [DX1033]
ATSAMD10D14A@QFN24 [DX4012]
ATSAMD10D14A@SOP20 [DX1033]
ATSAMD11C14A@SOP14 [DX1016]
ATSAMD11D14A@QFN24 [DX4012]
ATSAMD11D14A@SOP20 [DX1033]
ATSAMD20E14A@QFN32 [DX4015]
ATSAMD20E14A@TQFP32 [DX3001]
ATSAMD20E15A@QFN32 [DX4015]
ATSAMD20E15A@TQFP32 [DX3001]
ATSAMD20E16A@QFN32 [DX4015]
ATSAMD20E16A@TQFP32 [DX3001]
ATSAMD20E17A@QFN32 [DX4015]
ATSAMD20E17A@TQFP32 [DX3001]
ATSAMD20E18A@QFN32 [DX4015]
ATSAMD20E18A@TQFP32 [DX3001]
ATSAMD20G14A@QFN48 [DX4021]

ATSAMD20G14A@TQFP48 [DX3007]
ATSAMD20G15A@TQFP48 [DX3007]
ATSAMD20G16A@TQFP48 [DX3007]
ATSAMD20G17A@TQFP48 [DX3007]
ATSAMD20G18A@TQFP48 [DX3007]
ATSAMD20J14A@TQFP64 [DX3011]
ATSAMD20J15A@TQFP64 [DX3011]
ATSAMD20J16A@TQFP64 [DX3011]
ATSAMD20J17A@TQFP64 [DX3011]
ATSAMD20J18A@QFN64 [DX4023]
ATSAMD20J18A@UFBGA64 [DX5141]
ATSAMD21E15A@TQFP32 [DX3001]
ATSAMD21E16A@TQFP32 [DX3001]
ATSAMD21E17A@TQFP32 [DX3001]
ATSAMD21E18A@TQFP32 [DX3001]
ATSAMD21G15A@TQFP48 [DX3007]
ATSAMD21G16A@TQFP48 [DX3007]
ATSAMD21G17A@TQFP48 [DX3007]
ATSAMD21G18A@TQFP48 [DX3007]
ATSAMD21J15A@TQFP64 [DX3011]
ATSAMD21J16A@TQFP64 [DX3011]
ATSAMD21J17A@TQFP64 [DX3011]
ATSAMD21J18A@TQFP64 [DX3011]
ATSAMR21E17A@QFN32 [DX4015]
ATSAMR21G16A@QFN48 [DX4021]
ATSAMR21G18A@QFN48 [DX4021]
ATSHA204A-SSHDA@SOIC8 [DX1045]
ATSHA204-MAH-CZ@QFN8 [DX4002]
ATSHA204-SH-CZ@SOIC8 [DX1045]
ATSHA204-TH-CZ@TSSOP8 [DX1000]
ATtiny10 [DX0001]
ATtiny10@SOIC8 [DX1031]
ATtiny10@SOT23 [DX1041]
ATtiny10@UDFN8 [DX4035]
ATtiny11(ISP) [DX0001]
ATtiny11@SOIC8(ISP) [DX0001]
ATtiny11L(ISP) [DX0001]
ATtiny11L@SOIC8(ISP) [DX0001]
ATtiny12(ISP) [DX0001]
ATtiny12@SOIC8(ISP) [DX0001]
ATtiny12L(ISP) [DX0001]
ATtiny12L@SOIC8(ISP) [DX0001]
ATtiny12V(ISP) [DX0001]
ATtiny12V@SOIC8(ISP) [DX0001]
ATtiny13(ISP) [DX0001]
ATtiny13@MLF10(ISP) [DX0001]
ATtiny13@MLF20(ISP) [DX0001]
ATtiny13@SOIC8(3.9*6.2)(ISP) [DX0001]
ATSAMD20G15A@QFN48 [DX4021]
ATSAMD20G16A@QFN48 [DX4021]
ATSAMD20G17A@QFN48 [DX4021]
ATSAMD20G18A@QFN48 [DX4021]
ATSAMD20J14A@QFN64 [DX4023]
ATSAMD20J15A@QFN64 [DX4023]
ATSAMD20J16A@QFN64 [DX4023]
ATSAMD20J17A@QFN64 [DX4023]
ATSAMD20J17A@UFBGA64 [DX5141]
ATSAMD20J18A@TQFP64 [DX3011]
ATSAMD21E15A@QFN32 [DX4015]
ATSAMD21E16A@QFN32 [DX4015]
ATSAMD21E17A@QFN32 [DX4015]
ATSAMD21E18A@QFN32 [DX4015]
ATSAMD21G15A@QFN48 [DX4021]
ATSAMD21G16A@QFN48 [DX4021]
ATSAMD21G17A@QFN48 [DX4021]
ATSAMD21G18A@QFN48 [DX4021]
ATSAMD21J15A@QFN64 [DX4023]
ATSAMD21J16A@QFN64 [DX4023]
ATSAMD21J17A@QFN64 [DX4023]
ATSAMD21J18A@QFN64 [DX4023]
ATSAMR21E16A@QFN32 [DX4015]
ATSAMR21E18A@QFN32 [DX4015]
ATSAMR21G17A@QFN48 [DX4021]
ATSHA204A-MAHDA@QFN8 [DX4002]
ATSHA204A-XHDA@TSSOP8 [DX1000]
ATSHA204-MAH-DA@QFN8 [DX4002]
ATSHA204-SH-DA@SOIC8 [DX1045]
ATSHA204-TH-DA@TSSOP8 [DX1000]
ATtiny10(ISP) [DX0001]
ATtiny10@SOIC8(ISP) [DX0001]
ATtiny10@SOT23(ISP) [DX0001]
ATtiny11 [DX0001]
ATtiny11@SOIC8 [DX1031]
ATtiny11L [DX0001]
ATtiny11L@SOIC8 [DX1031]
ATtiny12 [DX0001]
ATtiny12@SOIC8 [DX1031]
ATtiny12L [DX0001]
ATtiny12L@SOIC8 [DX1031]
ATtiny12V [DX0001]
ATtiny12V@SOIC8 [DX1031]
ATtiny13 [DX0001]
ATtiny13@MLF10 [DX4007]
ATtiny13@MLF20 [DX4011]
ATtiny13@SOIC8(3.9*6.2) [DX1016]

ATtiny13@SOIC8(5.5*8.0) [DX1031]
ATtiny13@SOIC8(5.5*8.0)(ISP) [DX0001]
ATtiny13A [DX0001]
ATtiny13A@MLF10 [DX4007]
ATtiny13A@MLF20 [DX4011]
ATtiny13A@SOIC8(3.9*6.2) [DX1016]
ATtiny13A@SOIC8(5.5*8.0) [DX1031]
ATtiny13V [DX0001]
ATtiny13V(ISP) [DX0001]
ATtiny13V@MLF10 [DX4007]
ATtiny13V@MLF10(ISP) [DX0001]
ATtiny13V@MLF20 [DX4011]
ATtiny13V@MLF20(ISP) [DX0001]
ATtiny13V@SOIC8(3.9*6.2) [DX1016]
ATtiny13V@SOIC8(3.9*6.2)(ISP) [DX0001]
ATtiny13V@SOIC8(5.5*8.0) [DX1031]
ATtiny13V@SOIC8(5.5*8.0)(ISP) [DX0001]
ATtiny15 [DX0001]
ATtiny15(ISP) [DX0001]
ATtiny15@SOIC8 [DX1031]
ATtiny15@SOIC8(ISP) [DX0001]
ATtiny15L [DX0001]
ATtiny15L(ISP) [DX0001]
ATtiny15L@SOIC8 [DX1031]
ATtiny15L@SOIC8(ISP) [DX0001]
ATtiny1634@QFN20 [DX4011]
ATtiny1634@SOIC20 [DX1033]
ATtiny167@QFN32 [DX4015]
ATtiny167@QFN32(ISP) [DX0001]
ATtiny167@SOIC20 [DX1033]
ATtiny167@SOIC20(ISP) [DX0001]
ATtiny167@TSSOP20 [DX1000]
ATtiny167@TSSOP20(ISP) [DX0001]
ATtiny20@QFN20 [DX4044]
ATtiny20@SOIC14 [DX1016]
ATtiny20@TSSOP14 [DX1000]
ATtiny2313 [DX0001]
ATtiny2313(ISP) [DX0001]
ATtiny2313@MLF20 [DX4011]
ATtiny2313@QFN20(ISP) [DX0001]
ATtiny2313@SOIC20 [DX1033]
ATtiny2313@SOIC20(ISP) [DX0001]
ATtiny2313A [DX0001]
ATtiny2313A@QFN20 [DX4011]
ATtiny2313A@SOIC20 [DX1033]
ATtiny2313V [DX0001]
ATtiny2313V(ISP) [DX0001]
ATtiny2313V@MLF20 [DX4011]
ATtiny2313V@QFN20(ISP) [DX0001]
ATtiny2313V@SOIC20 [DX1033]
ATtiny2313V@SOIC20(ISP) [DX0001]
ATtiny24 [DX0001]
ATtiny24(ISP) [DX0001]
ATtiny24(low vol isp) [DX0001]
ATtiny24@MLF20 [DX4011]
ATtiny24@MLF20(ISP) [DX0001]
ATtiny24@MLF20(low vol isp) [DX0001]
ATtiny24@SOIC14 [DX1016]
ATtiny24@SOIC14(ISP) [DX0001]
ATtiny24@SOIC14(low vol isp) [DX0001]
ATtiny24A [DX0001]
ATtiny24A@MLF20(3*3) [DX4044]
ATtiny24A@MLF20(4*4) [DX4011]
ATtiny24A@SOIC14 [DX1016]
ATtiny24V [DX0001]
ATtiny24V(ISP) [DX0001]
ATtiny24V(low vol isp) [DX0001]
ATtiny24V@MLF20 [DX4011]
ATtiny24V@MLF20(ISP) [DX0001]
ATtiny24V@MLF20(low vol isp) [DX0001]
ATtiny24V@SOIC14 [DX1016]
ATtiny24V@SOIC14(ISP) [DX0001]
ATtiny24V@SOIC14(low vol isp) [DX0001]
ATtiny25 [DX0001]
ATtiny25(ISP) [DX0001]
ATtiny25(low vol isp) [DX0001]
ATtiny25@MLF20 [DX4011]
ATtiny25@MLF20(ISP) [DX0001]
ATtiny25@MLF20(low vol isp) [DX0001]

ATtiny25@SOIC8 [DX1031]
ATtiny25@SOIC8(ISP) [DX0001]
ATtiny25@SOIC8(low vol isp) [DX0001]
ATtiny25V [DX0001]
ATtiny25V(ISP) [DX0001]
ATtiny25V(low vol isp) [DX0001]
ATtiny25V@MLF20 [DX4011]
ATtiny25V@MLF20(ISP) [DX0001]
ATtiny25V@MLF20(low vol isp) [DX0001]
ATtiny25V@SOIC8 [DX1031]
ATtiny25V@SOIC8(ISP) [DX0001]
ATtiny25V@SOIC8(low vol isp) [DX0001]
ATtiny26 [DX0001]
ATtiny26(ISP) [DX0001]
ATtiny26(new) [DX0001]
ATtiny26(new)(ISP) [DX0001]
ATtiny26(new)@MLF32 [DX4015]
ATtiny26(new)@SOIC20 [DX1033]
ATtiny26(new)@SOIC20(ISP) [DX0001]
ATtiny26(new)@TSSOP20 [DX1000]
ATtiny26(new)@TSSOP20(ISP) [DX0001]
ATtiny26@MLF32 [DX4015]
ATtiny26@MLF32(ISP) [DX0001]
ATtiny26@SOIC20 [DX1033]
ATtiny26@SOIC20(ISP) [DX0001]
ATtiny26@TSSOP20 [DX1000]
ATtiny26@TSSOP20(ISP) [DX0001]
ATtiny261 [DX0001]
ATtiny261(ISP) [DX0001]
ATtiny261@MLF32 [DX4015]
ATtiny261@MLF32(ISP) [DX0001]
ATtiny261@SOIC20 [DX1033]
ATtiny261@SOIC20(ISP) [DX0001]
ATtiny261A [DX0001]
ATtiny261A(ISP) [DX0001]
ATtiny261A@MLF32 [DX4015]
ATtiny261A@MLF32(ISP) [DX0001]
ATtiny261A@SOIC20 [DX1033]
ATtiny261A@SOIC20(ISP) [DX0001]
ATtiny261V [DX0001]
ATtiny261V(ISP) [DX0001]
ATtiny261V@MLF32 [DX4015]
ATtiny261V@MLF32(ISP) [DX0001]
ATtiny261V@SOIC20 [DX1033]
ATtiny261V@SOIC20(ISP) [DX0001]
ATtiny26L [DX0001]
ATtiny26L(ISP) [DX0001]
ATtiny26L(new) [DX0001]
ATtiny26L(new)(ISP) [DX0001]
ATtiny26L(new)@MLF32 [DX4015]
ATtiny26L(new)@SOIC20 [DX1033]
ATtiny26L(new)@SOIC20(ISP) [DX0001]
ATtiny26L(new)@TSSOP20 [DX1000]
ATtiny26L(new)@TSSOP20(ISP) [DX0001]
ATtiny26L@MLF32 [DX4015]
ATtiny26L@MLF32(ISP) [DX0001]
ATtiny26L@SOIC20 [DX1033]
ATtiny26L@SOIC20(ISP) [DX0001]
ATtiny26L@TSSOP20 [DX1000]
ATtiny26L@TSSOP20(ISP) [DX0001]
ATtiny26LN@MLF32(ISP) [DX0001]
ATtiny26N@MLF32(ISP) [DX0001]
ATtiny28L [DX0001]
ATtiny28L@MLF32 [DX4015]
ATtiny28L@TQFP32 [DX3001]
ATtiny28V [DX0001]
ATtiny28V@MLF32 [DX4015]
ATtiny28V@TQFP32 [DX3001]
ATtiny4@SOT23 [DX1041]
ATtiny4@UDFN8 [DX4035]
ATtiny40@QFN20 [DX4044]
ATtiny40@SOIC20 [DX1033]
ATtiny40@TSSOP20 [DX1000]
ATtiny4313 [DX0001]
ATtiny4313@QFN20 [DX4011]
ATtiny4313@SOIC20 [DX1033]
ATtiny43U@MLF20 [DX4011]
ATtiny43U@SOIC20 [DX1033]
ATtiny44 [DX0001]
ATtiny44(ISP) [DX0001]
ATtiny44(low vol isp) [DX0001]
ATtiny44@MLF20 [DX4011]
ATtiny44@MLF20(ISP) [DX0001]
ATtiny44@MLF20(low vol isp) [DX0001]

ATtiny44@SOIC14 [DX1016]　　ATtiny44@SOIC14(ISP) [DX0001]
ATtiny44@SOIC14(low vol isp) [DX0001]
ATtiny44A [DX0001]　　ATtiny44A@MLF20(3*3) [DX4044]
ATtiny44A@MLF20(4*4) [DX4011]　　ATtiny44A@SOIC14 [DX1016]
ATtiny44V [DX0001]　　ATtiny44V(ISP) [DX0001]
ATtiny44V(low vol isp) [DX0001]　　ATtiny44V@MLF20 [DX4011]
ATtiny44V@MLF20(ISP) [DX0001]
ATtiny44V@MLF20(low vol isp) [DX0001]
ATtiny44V@SOIC14 [DX1016]　　ATtiny44V@SOIC14(ISP) [DX0001]
ATtiny44V@SOIC14(low vol isp) [DX0001]
ATtiny45 [DX0001]　　ATtiny45(ISP) [DX0001]
ATtiny45(low vol isp) [DX0001]　　ATtiny45@MLF20 [DX4011]
ATtiny45@MLF20(ISP) [DX0001]
ATtiny45@MLF20(low vol isp) [DX0001]
ATtiny45@SOIC8 [DX1031]　　ATtiny45@SOIC8(ISP) [DX0001]
ATtiny45@SOIC8(low vol isp) [DX0001]
ATtiny45V [DX0001]　　ATtiny45V(ISP) [DX0001]
ATtiny45V(low vol isp) [DX0001]　　ATtiny45V@MLF20 [DX4011]
ATtiny45V@MLF20(ISP) [DX0001]
ATtiny45V@MLF20(low vol isp) [DX0001]
ATtiny45V@SOIC8 [DX1031]　　ATtiny45V@SOIC8(ISP) [DX0001]
ATtiny45V@SOIC8(low vol isp) [DX0001]
ATtiny461 [DX0001]　　ATtiny461(ISP) [DX0001]
ATtiny461@MLF32 [DX4015]　　ATtiny461@MLF32(ISP) [DX0001]
ATtiny461@SOIC20 [DX1033]　　ATtiny461@SOIC20(ISP) [DX0001]
ATtiny461A [DX0001]　　ATtiny461A(ISP) [DX0001]
ATtiny461A@MLF32 [DX4015]　　ATtiny461A@MLF32(ISP) [DX0001]
ATtiny461A@SOIC20 [DX1033]　　ATtiny461A@SOIC20(ISP) [DX0001]
ATtiny461V [DX0001]　　ATtiny461V(ISP) [DX0001]
ATtiny461V@MLF32 [DX4015]　　ATtiny461V@MLF32(ISP) [DX0001]
ATtiny461V@SOIC20 [DX1033]　　ATtiny461V@SOIC20(ISP) [DX0001]
ATtiny48 [DX0001]　　ATtiny48(ISP) [DX0001]
ATtiny48@MLF28 [DX4033]　　ATtiny48@MLF28(ISP) [DX0001]
ATtiny48@MLF32 [DX4015]　　ATtiny48@MLF32(ISP) [DX0001]
ATtiny48@TQFP32 [DX3001]　　ATtiny48@TQFP32(ISP) [DX0001]
ATtiny48V [DX0001]　　ATtiny48V(ISP) [DX0001]
ATtiny48V@MLF28 [DX4033]　　ATtiny48V@MLF28(ISP) [DX0001]
ATtiny48V@MLF32 [DX4015]　　ATtiny48V@MLF32(ISP) [DX0001]
ATtiny48V@TQFP32 [DX3001]　　ATtiny48V@TQFP32(ISP) [DX0001]
ATtiny5@SOT23 [DX1041]　　ATtiny5@UDFN8 [DX4035]
ATtiny828@MLF32 [DX4015]　　ATtiny828@TQFP32 [DX3001]
ATtiny84 [DX0001]　　ATtiny84(ISP) [DX0001]
ATtiny84(low vol isp) [DX0001]　　ATtiny84@MLF20 [DX4011]
ATtiny84@MLF20(ISP) [DX0001]
ATtiny84@MLF20(low vol isp) [DX0001]
ATtiny84@SOIC14 [DX1016]　　ATtiny84@SOIC14(ISP) [DX0001]
ATtiny84@SOIC14(low vol isp) [DX0001]
ATtiny84A [DX0001]　　ATtiny84A@MLF20(3*3) [DX4044]

ATtiny84A@MLF20(4*4) [DX4011]
ATtiny84A@SOIC14 [DX1016]
ATtiny84V [DX0001]
ATtiny84V(ISP) [DX0001]
ATtiny84V(low vol isp) [DX0001]
ATtiny84V@MLF20 [DX4011]
ATtiny84V@MLF20(ISP) [DX0001]
ATtiny84V@MLF20(low vol isp) [DX0001]
ATtiny84V@SOIC14 [DX1016]
ATtiny84V@SOIC14(ISP) [DX0001]
ATtiny84V@SOIC14(low vol isp) [DX0001]
ATtiny85 [DX0001]
ATtiny85(ISP) [DX0001]
ATtiny85(low vol isp) [DX0001]
ATtiny85@MLF20 [DX4011]
ATtiny85@MLF20(ISP) [DX0001]
ATtiny85@MLF20(low vol isp) [DX0001]
ATtiny85@SOIC8 [DX1031]
ATtiny85@SOIC8(ISP) [DX0001]
ATtiny85@SOIC8(low vol isp) [DX0001]
ATtiny85V [DX0001]
ATtiny85V(ISP) [DX0001]
ATtiny85V(low vol isp) [DX0001]
ATtiny85V@MLF20 [DX4011]
ATtiny85V@MLF20(ISP) [DX0001]
ATtiny85V@MLF20(low vol isp) [DX0001]
ATtiny85V@SOIC8 [DX1031]
ATtiny85V@SOIC8(ISP) [DX0001]
ATtiny85V@SOIC8(low vol isp) [DX0001]
ATtiny861 [DX0001]
ATtiny861(ISP) [DX0001]
ATtiny861@MLF32 [DX4015]
ATtiny861@MLF32(ISP) [DX0001]
ATtiny861@SOIC20 [DX1033]
ATtiny861@SOIC20(ISP) [DX0001]
ATtiny861A [DX0001]
ATtiny861A(ISP) [DX0001]
ATtiny861A@MLF32 [DX4015]
ATtiny861A@MLF32(ISP) [DX0001]
ATtiny861A@SOIC20 [DX1033]
ATtiny861A@SOIC20(ISP) [DX0001]
ATtiny861V [DX0001]
ATtiny861V(ISP) [DX0001]
ATtiny861V@MLF32 [DX4015]
ATtiny861V@MLF32(ISP) [DX0001]
ATtiny861V@SOIC20 [DX1033]
ATtiny861V@SOIC20(ISP) [DX0001]
ATtiny87@QFN32 [DX4015]
ATtiny87@QFN32(ISP) [DX0001]
ATtiny87@SOIC20 [DX1033]
ATtiny87@SOIC20(ISP) [DX0001]
ATtiny87@TSSOP20 [DX1000]
ATtiny87@TSSOP20(ISP) [DX0001]
ATtiny88 [DX0001]
ATtiny88(ISP) [DX0001]
ATtiny88@MLF28 [DX4033]
ATtiny88@MLF28(ISP) [DX0001]
ATtiny88@MLF32 [DX4015]
ATtiny88@MLF32(ISP) [DX0001]
ATtiny88@TQFP32 [DX3001]
ATtiny88@TQFP32(ISP) [DX0001]
ATtiny88V [DX0001]
ATtiny88V(ISP) [DX0001]
ATtiny88V@MLF28 [DX4033]
ATtiny88V@MLF28(ISP) [DX0001]
ATtiny88V@MLF32 [DX4015]
ATtiny88V@MLF32(ISP) [DX0001]
ATtiny88V@TQFP32 [DX3001]
ATtiny88V@TQFP32(ISP) [DX0001]
ATtiny9@SOT23 [DX1041]
ATtiny9@UDFN8 [DX4035]
ATUC128D3@QFN64 [DX4023]
ATUC128D3@QFP64 [DX3011]
ATUC128D4@QFN48 [DX4021]
ATUC128D4@QFP48 [DX3007]
ATUC128L3U@QFN64 [DX4023]
ATUC128L3U@TQFP64 [DX3011]
ATUC128L4U@QFN48 [DX4021]
ATUC128L4U@TQFP48 [DX3007]
ATUC256L3U@QFN64 [DX4023]
ATUC256L3U@TQFP64 [DX3011]
ATUC256L4U@QFN48 [DX4021]
ATUC256L4U@TQFP48 [DX3007]
ATUC64D3@QFN64 [DX4023]
ATUC64D3@QFP64 [DX3011]
ATUC64D4@QFN48 [DX4021]
ATUC64D4@QFP48 [DX3007]

ATUC64L3U@QFN64 [DX4023]
ATUC64L4U@QFN48 [DX4021]
ATxmega128A1@BGA100 [DX5055]
ATxmega128A1U@CBGA100 [DX5055]
ATxmega128A1U@VFBGA100 [DX5215]
ATxmega128A3@TQFP64 [DX3044]
ATxmega128A3U@TQFP64 [DX3044]
ATxmega128A4@TQFP44 [DX3005]
ATxmega128A4U@QFN44 [DX4018]
ATxmega128B1@TQFP100 [DX3043]
ATxmega128B3@TQFP64 [DX3044]
ATxmega128C3@TQFP64 [DX3044]
ATxmega128D3@TQFP64 [DX3044]
ATxmega128D4@TQFP44 [DX3005]
ATxmega16A4@QFN44 [DX4018]
ATxmega16A4@VFBGA49 [DX5154]
ATxmega16A4U@QFN44 [DX4018]
ATxmega16C4@QFN44 [DX4018]
ATxmega16C4@VFBGA49 [DX5154]
ATxmega16D4@TQFP44 [DX3005]
ATxmega16E5@TQFP32 [DX3001]
ATxmega16E5@VQFN32 [DX4015]
ATxmega192A1@TQFP100 [DX3043]
ATxmega192A3@TQFP64 [DX3044]
ATxmega192A3U@TQFP64 [DX3044]
ATxmega192C3@TQFP64 [DX3044]
ATxmega192D3@TQFP64 [DX3044]
ATxmega256A1@TQFP100 [DX3043]
ATxmega256A3@TQFP64 [DX3044]
ATxmega256A3B@TQFP64 [DX3044]
ATxmega256A3BU@TQFP64 [DX3044]
ATxmega256A3U@TQFP64 [DX3044]
ATxmega256C3@TQFP64 [DX3044]
ATxmega256D3@TQFP64 [DX3044]
ATxmega32A4@TQFP44 [DX3005]
ATxmega32A4U@BGA49 [DX5154]
ATxmega32A4U@TQFP44 [DX3005]
ATxmega32C4@TQFP44 [DX3005]
ATxmega32D4@QFN44 [DX4018]
ATxmega32D4@VFBGA49 [DX5154]
ATxmega32E5@UQFN32 [DX4084]
ATxmega384C3@QFN64 [DX4023]
ATxmega64A1@BGA100 [DX5055]
ATxmega64A1U@CBGA100 [DX5055]
ATxmega64A1U@VFBGA100 [DX5215]
ATxmega64A3@TQFP64 [DX3044]
ATxmega64A3U@TQFP64 [DX3044]
ATxmega64A4@TQFP44 [DX3005]
ATUC64L3U@TQFP64 [DX3011]
ATUC64L4U@TQFP48 [DX3007]
ATxmega128A1@TQFP100 [DX3043]
ATxmega128A1U@TQFP100 [DX3043]
ATxmega128A3@QFN64 [DX4023]
ATxmega128A3U@QFN64 [DX4023]
ATxmega128A4@QFN44 [DX4018]
ATxmega128A4U@BGA49 [DX5154]
ATxmega128A4U@TQFP44 [DX3005]
ATxmega128B3@QFN64 [DX4023]
ATxmega128C3@QFN64 [DX4023]
ATxmega128D3@QFN64 [DX4023]
ATxmega128D4@QFN44 [DX4018]
ATxmega128D4@VFBGA49 [DX5154]
ATxmega16A4@TQFP44 [DX3005]
ATxmega16A4U@BGA49 [DX5154]
ATxmega16A4U@TQFP44 [DX3005]
ATxmega16C4@TQFP44 [DX3005]
ATxmega16D4@QFN44 [DX4018]
ATxmega16D4@VFBGA49 [DX5154]
ATxmega16E5@UQFN32 [DX4084]
ATxmega192A1@BGA100 [DX5055]
ATxmega192A3@QFN64 [DX4023]
ATxmega192A3U@QFN64 [DX4023]
ATxmega192C3@QFN64 [DX4023]
ATxmega192D3@QFN64 [DX4023]
ATxmega256A1@BGA100 [DX5055]
ATxmega256A3@QFN64 [DX4023]
ATxmega256A3B@QFN64 [DX4023]
ATxmega256A3BU@QFN64 [DX4023]
ATxmega256A3U@QFN64 [DX4023]
ATxmega256C3@QFN64 [DX4023]
ATxmega256D3@QFN64 [DX4023]
ATxmega32A4@QFN44 [DX4018]
ATxmega32A4@VFBGA49 [DX5154]
ATxmega32A4U@QFN44 [DX4018]
ATxmega32C4@QFN44 [DX4018]
ATxmega32C4@VFBGA49 [DX5154]
ATxmega32D4@TQFP44 [DX3005]
ATxmega32E5@TQFP32 [DX3001]
ATxmega32E5@VQFN32 [DX4015]
ATxmega384C3@TQFP64 [DX3044]
ATxmega64A1@TQFP100 [DX3043]
ATxmega64A1U@TQFP100 [DX3043]
ATxmega64A3@QFN64 [DX4023]
ATxmega64A3U@QFN64 [DX4023]
ATxmega64A4@QFN44 [DX4018]
ATxmega64A4U@BGA49 [DX5154]

ATxmega64A4U@QFN44 [DX4018]
ATxmega64A4U@TQFP44 [DX3005]
ATxmega64B1@TQFP100 [DX3043]
ATxmega64B3@QFN64 [DX4023]
ATxmega64B3@TQFP64 [DX3044]
ATxmega64C3@QFN64 [DX4023]
ATxmega64C3@TQFP64 [DX3044]
ATxmega64D3@QFN64 [DX4023]
ATxmega64D3@TQFP64 [DX3044]
ATxmega64D4@QFN44 [DX4018]
ATxmega64D4@TQFP44 [DX3005]
ATxmega64D4@VFBGA49 [DX5154]
ATxmega8E5@TQFP32 [DX3001]
ATxmega8E5@UQFN32 [DX4084]
ATxmega8E5@VQFN32 [DX4015]
T89C51SND1@TQFP80 [DX3018]
T89F64 [DX0001]
T89F64@PLCC44 [DX2044]
T89F64@TQFP44 [DX3003]

ATMEL W&M

MICROCONTROLLER

AT89C5115@PLCC28 [DX2028]
AT89C5115@SOIC28 [DX1033]
AT89C5115@TQFP32 [DX3001]
AT89C51CC02@PLCC28 [DX2028]
AT89C51CC02@SOIC28 [DX1033]
AT89C51CC02@TQFP32 [DX3001]
T89C5115@PLCC28 [DX2028]
T89C5115@SOIC28 [DX1033]
T89C5115@TQFP32 [DX3001]
T89C51AC2@PLCC44 [DX2044]
T89C51AC2@TQFP44 [DX3003]
T89C51CC01@PLCC44 [DX2044]
T89C51CC01@TQFP44 [DX3003]
T89C51CC02@PLCC28 [DX2028]
T89C51CC02@SOIC24 [DX1033]
T89C51CC02@SOIC28 [DX1033]
T89C51CC02@TQFP32 [DX3001]
T89C51IB2@PLCC44 [DX2044]
T89C51IB2@TQFP44 [DX3003]
T89C51IC2@PLCC44 [DX2044]
T89C51IC2@TQFP44 [DX3003]
T89C51RB2 [DX0001]
T89C51RB2@PLCC44 [DX2044]
T89C51RB2@TQFP44 [DX3003]
T89C51RC2 [DX0001]
T89C51RC2@PLCC44 [DX2044]
T89C51RC2@TQFP44 [DX3003]
T89C51RD2 [DX0001]
T89C51RD2@PLCC44 [DX2044]
T89C51RD2@PLCC68 [DX2068]
T89C51RD2@TQFP44 [DX3003]
T89F64 [DX0001]
T89F64@PLCC44 [DX2044]
T89F64@TQFP44 [DX3003]
TS87C51RB2 [DX0001]
TS87C51RB2@PLCC44 [DX2044]
TS87C51RB2@TQFP44 [DX3002]
TS87C51RC2 [DX0001]
TS87C51RC2@PLCC44 [DX2044]
TS87C51RC2@TQFP44 [DX3002]
TS87C51RD2 [DX0001]
TS87C51RD2@PLCC44 [DX2044]
TS87C51RD2@TQFP44 [DX3002]
TS87C51U2 [DX0001]
TS87C51U2@PLCC44 [DX2044]
TS87C51U2@TQFP44 [DX3002]
TS87C52X2 [DX0001]
TS87C52X2@PLCC44 [DX2044]
TS87C52X2@TQFP44 [DX3002]
TS87C54X2 [DX0001]
TS87C54X2@PLCC44 [DX2044]
TS87C54X2@TQFP44 [DX3002]
TS87C58X2 [DX0001]
TS87C58X2@PLCC44 [DX2044]
TS87C58X2@TQFP44 [DX3002]
TSC87251A1@PLCC44 [DX2044]
TSC87251G1 [DX0001]
TSC87251G1@PLCC44 [DX2004]
TSC87251G1A [DX0001]
TSC87251G1A@PLCC44 [DX2044]
TSC87251G2D [DX0001]
TSC87251G2D@PLCC44 [DX2044]
TSC87251G2D@TQFP44 [DX3003]
TSC87C51 [DX0001]

TSC87C51@PLCC44 [DX2044]
TSC87C51@TQFP44 [DX3002]

ATMEL-CUSTOM

MICROCONTROLLER

ATMEGA48(ISP)(CAL) [DX0001]
ATMEGA48@TQFP32(CAL) [DX3061]
ATMEGA48PA(ISP)(CAL) [DX0001]
ATMEGA48PA@TQFP32(CAL) [DX3061]
ATMEGA48PV(ISP)(CAL) [DX0001]
ATMEGA48PV@TQFP32(CAL) [DX3061]
ATMEGA88PA@MLF32 [DX4015]

ATMEL-CUSTOMER

E(E)PROM/FRAM/NVRAM

AT88SC018CM(intusurg) [DX1045]

MICROCONTROLLER

AT90CAN128@QFN64 [DX4023]
AT90CAN128@TQFP64 [DX3013]
AT90CAN64@QFN64 [DX4023]
AT90CAN64@TQFP64 [DX3013]

ATO

E(E)PROM/FRAM/NVRAM

AFND1208U1@TSOP48 [DX1004-3]
AFND1G08U3@TSOP48 [DX1004-3]
AFND5608S1@TSOP48 [DX1004-3]
AFND5608U1@TSOP48 [DX1004-3]
MST8A08B16FMHF@FBGA107 [DX5028]
MST8B08B16FMHF@FBGA107 [DX5028]
MST8B08B32FMH@FBGA137 [DX5011]
MST9B08B16FMHF@FBGA107 [DX5028]
MST9B16B16FMHC@BGA130 [DX5140-1]
MST9D08D16FMHC@BGA130 [DX5140-1]
MST9D08D16FMHF@BGA107 [DX5028]
MST9D08D32FMH@BGA137 [DX5011-1]
MST9D16D16FMHC@BGA130 [DX5140-1]
MST9F08F32FMH@BGA137 [DX5011-1]
MST9F08F32FMHC@BGA130 [DX5140-1]
MST9F16F16FMHC@BGA130 [DX5140-1]
MST9F16F32FMH@BGA137 [DX5011-1]

AUO

E(E)PROM/FRAM/NVRAM

AUO-G1422.29@TQFN32 [DX4015]
AUO-G1422.2H@TQFN32 [DX4015]

AUSTIN

E(E)PROM/FRAM/NVRAM

AS8E512K8 [DX0001]
AS8E512K8@SOJ32 [DX1038]

AUX

MICROCONTROLLER

R5F104JFAFA@QFP52 [DX3010]

AXELITE

E(E)PROM/FRAM/NVRAM

AX24C02A@DFN8 [DX4047]
AX24C02A@SOP8 [DX1045]
AX24C02A@SOT23-5 [DX1041]
AX24C02A@TSSOP8 [DX1059]
AX24C04A@DFN8 [DX4047]
AX24C04A@SOP8 [DX1045]
AX24C04A@SOT23-5 [DX1041]
AX24C04A@TSSOP8 [DX1059]
AX24C08A@DFN8 [DX4047]
AX24C08A@SOP8 [DX1045]
AX24C08A@SOT23-5 [DX1041]
AX24C08A@TSSOP8 [DX1059]
AX24C128A@DFN8 [DX4047]
AX24C128A@SOP8 [DX1045]
AX24C128A@TSSOP8 [DX1059]
AX24C16A@DFN8 [DX4047]
AX24C16A@SOP8 [DX1045]
AX24C16A@SOT23-5 [DX1041]
AX24C16A@TSSOP8 [DX1059]
AX24C256A@DFN8 [DX4047]
AX24C256A@SOP8 [DX1045]
AX24C256A@TSSOP8 [DX1059]
AX24C32A@DFN8 [DX4047]
AX24C32A@SOP8 [DX1045]
AX24C32A@TSSOP8 [DX1059]
AX24C64A@DFN8 [DX4047]
AX24C64A@SOP8 [DX1045]
AX24C64A@TSSOP8 [DX1059]

AZOTEQ

MICROCONTROLLER

IQS512@TSSOP20 [DX1067-4]
IQS525@QFN28 [DX4083-3]
IQS530@TSSOP20 [DX1067-4]
IQS550@QFN48 [DX4021-2]
IQS572@QFN28 [DX4083-3]

BB

MICROCONTROLLER

MSC1210Y2PAGR [DX3057]
MSC1210Y3PAGR [DX3057]
MSC1210Y4PAGR [DX3057]
MSC1210Y5PAGR [DX3057]
MSC1211Y2PAGR [DX3057]
MSC1211Y3PAGR [DX3057]

MSC1211Y4PAGR [DX3057]
MSC1211Y5PAGR [DX3057]
MSC1212Y2PAGR [DX3057]
MSC1212Y3PAGR [DX3057]
MSC1212Y4PAGR [DX3057]
MSC1212Y5PAGR [DX3057]
MSC1213Y2PAGR [DX3057]
MSC1213Y3PAGR [DX3057]
MSC1213Y4PAGR [DX3057]
MSC1213Y5PAGR [DX3057]
MSC1214Y2PAGR [DX3057]
MSC1214Y3PAGR [DX3057]
MSC1214Y4PAGR [DX3057]
MSC1214Y5PAGR [DX3057]

BEKEN

MICROCONTROLLER

BK3231@QFN32 [DX4084-ZXL1]
BK3231@QFN32(Left Down) [DX4084-ZXL3]
BK3231QB@QFN56 [DX4089-ZXL1]
BK3231QB@QFN56(Left Down) [DX4089-ZXL2]
BK3431@QFN32 [DX4084-ZXL2]
BK3431@QFN32(Left Down) [DX4084-ZXL4]

BELLING

E(E)PROM/FRAM/NVRAM

BL24C02 [DX0001]
BL24C02@SOP8 [DX1045]
BL24C02@TSSOP8 [DX1059]
BL24C04 [DX0001]
BL24C04@SOP8 [DX1045]
BL24C04@TSSOP8 [DX1059]
BL24C08 [DX0001]
BL24C08@SOP8 [DX1045]
BL24C08@TSSOP8 [DX1059]
BL24C128 [DX0001]
BL24C128@SOP8 [DX1045]
BL24C128@TSSOP8 [DX1059]
BL24C16 [DX0001]
BL24C16@SOP8 [DX1045]
BL24C16@TSSOP8 [DX1059]
BL24C256 [DX0001]
BL24C256@SOP8 [DX1045]
BL24C256@TSSOP8 [DX1059]
BL24C32 [DX0001]
BL24C32@SOP8 [DX1045]
BL24C32@TSSOP8 [DX1059]
BL24C512 [DX0001]
BL24C512@SOP8 [DX1045]
BL24C512@TSSOP8 [DX1059]
BL24C64 [DX0001]
BL24C64@SOP8 [DX1045]
BL24C64@TSSOP8 [DX1059]

BENCHMARQ

E(E)PROM/FRAM/NVRAM

BQ3285 [DX0001]
BQ3287 [DX0001]
BQ3287A [DX0001]
BQ4010 [DX0001]
BQ4010Y [DX0001]
BQ4011 [DX0001]

BQ4011Y [DX0001]
BQ4013Y [DX0001]
BQ4014Y [DX0001]
BQ4015Y [DX0001]
BQ4822Y [DX0001]
BQ4832Y [DX0001]
BQ4013 [DX0001]
BQ4014 [DX0001]
BQ4015 [DX0001]
BQ4822 [DX0001]
BQ4830Y [DX0001]
BQ4842Y [DX0001]

BERGMICRO

E(E)PROM/FRAM/NVRAM

BG25Q10A@SOIC8[150 mil] [DX1045#1]
BG25Q10A@SOIC8[200 mil] [DX1044#1]
BG25Q16A [DX0001]
BG25Q16A@SOP8 [DX1044#1]
BG25Q20A@SOIC8[150 mil] [DX1045#1]
BG25Q20A@SOIC8[200 mil] [DX1044#1]
BG25Q32A@SOIC8[150 mil] [DX1044#1]
BG25Q32A@SOIC8[200 mil] [DX1044#1]
BG25Q40A [DX0001]
BG25Q40A@SOP8[150mil] [DX1045#1]
BG25Q40A@SOP8[200mil] [DX1044#1]
BG25Q40A@WSON8 [DX4005#1]
BG25Q512A@SOP8[150mil] [DX1045#1]
BG25Q512A@SOP8[200mil] [DX1044#1]
BG25Q80A [DX0001]
BG25Q80A@SOP8[150mil] [DX1045#1]
BG25Q80A@SOP8[200mil] [DX1044#1]
BG25Q80A@WSON8 [DX4005#1]

BILWAY

MICROCONTROLLER

EP94Z1E@QFP64 [DX3085-2]
EPF011C [DX1025-1]
EPF021A@QFP64 [DX3085-1]
EPF025A@QFP64 [DX3085-1]
EPF011A [DX3057-11]
EPF011D [DX3127]
EPF021D@QFP48 [DX3127]
EPF025R [DX3085-1]

BJX

E(E)PROM/FRAM/NVRAM

BJX24LC02 [DX0001]
BJX24LC02@TSSOP8 [DX1059]
BJX24LC04@SOIC8 [DX1045]
BJX24LC08 [DX0001]
BJX24LC08@TSSOP8 [DX1059]
BJX24LC16@SOIC8 [DX1045]
BJX24LC02@SOIC8 [DX1045]
BJX24LC04 [DX0001]
BJX24LC04@TSSOP8 [DX1059]
BJX24LC08@SOIC8 [DX1045]
BJX24LC16 [DX0001]
BJX24LC16@TSSOP8 [DX1059]

BMT

E(E)PROM/FRAM/NVRAM

BM29LV160B@FBGA48 [DX5043]
BM29LV160T@FBGA48 [DX5043]
BM29LV160B@TSOP48 [DX1004]
BM29LV160T@TSOP48 [DX1004]

BOCH

MICROCONTROLLER

CY8C24533 [DX0001]

Bookly Micro

E(E)PROM/FRAM/NVRAM

24C02 [DX0001]
24C02@DFN8 [DX4047]
24C02@MSOP8 [DX1015]
24C02@SOIC8 [DX1045]
24C02@TSSOP8 [DX1059]
24C04 [DX0001]
24C04@DFN8 [DX4047]
24C04@MSOP8 [DX1015]
24C04@SOIC8 [DX1045]
24C04@TSSOP8 [DX1059]
24C08 [DX0001]
24C08@DFN8 [DX4047]
24C08@MSOP8 [DX1015]
24C08@SOIC8 [DX1045]
24C08@TSSOP8 [DX1059]
24C16 [DX0001]
24C16@DFN8 [DX4047]
24C16@MSOP8 [DX1015]
24C16@SOIC8 [DX1045]
24C16@TSSOP8 [DX1059]

BRIGHT

E(E)PROM/FRAM/NVRAM

BM29F040 [DX0001]
BM29F040@PLCC32 [DX2032]
BM29F040@TSOP32 [DX1002]
BM29F400B@PSOP44 [DX1014]
BM29F400B@TSOP48 [DX1004]
BM29F400T@PSOP44 [DX1014]
BM29F400T@TSOP48 [DX1004]

CATALYST

E(E)PROM/FRAM/NVRAM

CAT1021(L) [DX0001]
CAT1021(P) [DX0001]
CAT1021(R)@MSOP8 [DX1059]
CAT1021(S)@SOIC8 [DX1045]
CAT1021(U)@TSSOP8 [DX1059]
CAT1021(V)@SOIC8 [DX1045]
CAT1021(Y)@TSSOP8 [DX1059]
CAT1021(Z)@MSOP8 [DX1059]

CAT1022(L) [DX0001]
CAT1022(P) [DX0001]
CAT1022(R)@MSOP8 [DX1059]
CAT1022(S)@SOIC8 [DX1045]
CAT1022(U)@TSSOP8 [DX1059]
CAT1022(V)@SOIC8 [DX1045]
CAT1022(Y)@TSSOP8 [DX1059]
CAT1022(Z)@MSOP8 [DX1059]
CAT1023(L) [DX0001]
CAT1023(P) [DX0001]
CAT1023(R)@MSOP8 [DX1059]
CAT1023(S)@SOIC8 [DX1045]
CAT1023(U)@TSSOP8 [DX1059]
CAT1023(V)@SOIC8 [DX1045]
CAT1023(Y)@TSSOP8 [DX1059]
CAT1023(Z)@MSOP8 [DX1059]
CAT1024(L) [DX0001]
CAT1024(P) [DX0001]
CAT1024(R)@MSOP8 [DX1059]
CAT1024(S)@SOIC8 [DX1045]
CAT1024(U)@TSSOP8 [DX1059]
CAT1024(V)@SOIC8 [DX1045]
CAT1024(Y)@TSSOP8 [DX1059]
CAT1024(Z)@MSOP8 [DX1059]
CAT1025(L) [DX0001]
CAT1025(P) [DX0001]
CAT1025(R)@MSOP8 [DX1059]
CAT1025(S)@SOIC8 [DX1045]
CAT1025(U)@TSSOP8 [DX1059]
CAT1025(V)@SOIC8 [DX1045]
CAT1025(Y)@TSSOP8 [DX1059]
CAT1025(Z)@MSOP8 [DX1059]
CAT1026(L) [DX0001]
CAT1026(P) [DX0001]
CAT1026(R)@MSOP8 [DX1059]
CAT1026(S)@SOIC8 [DX1045]
CAT1026(U)@TSSOP8 [DX1059]
CAT1026(V)@SOIC8 [DX1045]
CAT1026(Y)@TSSOP8 [DX1059]
CAT1026(Z)@MSOP8 [DX1059]
CAT1027(L) [DX0001]
CAT1027(P) [DX0001]
CAT1027(R)@MSOP8 [DX1059]
CAT1027(S)@SOIC8 [DX1045]
CAT1027(U)@TSSOP8 [DX1059]
CAT1027(V)@SOIC8 [DX1045]
CAT1027(Y)@TSSOP8 [DX1059]
CAT1027(Z)@MSOP8 [DX1059]
CAT1161(J)@SOIC8 [DX1045]
CAT1161(P) [DX0001]
CAT1162(J)@SOIC8 [DX1045]
CAT1162(P) [DX0001]
CAT1163(J)@SOIC8 [DX1045]
CAT1163(P) [DX0001]
CAT1320 [DX0001]
CAT1320@SOIC8 [DX1045]
CAT1320@TDFN8 [DX0001]
CAT1320@TSSOP8 [DX1059]
CAT1321 [DX0001]
CAT1321@SOIC8 [DX1045]
CAT1321@TDFN8 [DX0001]
CAT1321@TSSOP8 [DX1059]
CAT14002@SOIC8 [DX1045]
CAT14004@SOIC8 [DX1045]
CAT14008@SOIC8 [DX1045]
CAT14016@SOIC8 [DX1045]
CAT15002@SOIC8 [DX1045]
CAT15004@SOIC8 [DX1045]
CAT15008@SOIC8 [DX1045]
CAT15016@SOIC8 [DX1045]
CAT1640 [DX0001]
CAT1640@SOIC8 [DX1045]
CAT1640@TDFN8 [DX0001]
CAT1640@TSSOP8 [DX1059]
CAT1641 [DX0001]
CAT1641@SOIC8 [DX1045]
CAT1641@TDFN8 [DX0001]
CAT1641@TSSOP8 [DX1059]
CAT2210 [DX0001]
CAT2210@SOIC16 [DX1033]
CAT2210I [DX0001]
CAT2210I@SOIC16 [DX1033]
CAT2212 [DX0001]
CAT2212@SOIC20 [DX1033]
CAT2212I [DX0001]
CAT2212I@SOIC20 [DX1033]
CAT22C10 [DX0001]
CAT22C10@SOIC16 [DX1033]
CAT22C10I [DX0001]
CAT22C10I@SOIC16 [DX1033]
CAT22C12 [DX0001]
CAT22C12@SOIC20 [DX1033]
CAT22C12I [DX0001]
CAT22C12I@SOIC20 [DX1033]
CAT24AA01@SOIC8 [DX1045]
CAT24AA01@TSOT-23 [DX1041]

CAT24AA02@SOIC8 [DX1045]
CAT24AA02@TSOT-23 [DX1041]
CAT24AA04@SOIC8 [DX1045]
CAT24AA04@TSOT-23 [DX1041]
CAT24AA08@SOIC8 [DX1045]
CAT24AA08@TSOT-23 [DX1041]
CAT24AA16@SOIC8 [DX1045]
CAT24AA16@TSOT-23 [DX1041]
CAT24AC128 [DX0001]
CAT24AC128@SOIC8 [DX1045]
CAT24AC128@TSSOP14 [DX1000]
CAT24AC128@TSSOP8 [DX1059]
CAT24AC128@UDFN8 [DX4047]
CAT24C00 [DX0001]
CAT24C00@SOIC8 [DX1045]
CAT24C00@TSSOP8 [DX1059]
CAT24C01 [DX0001]
CAT24C01@MSOP8 [DX1015]
CAT24C01@SOIC14 [DX1030]
CAT24C01@SOIC8 [DX1045]
CAT24C01@TDFN8 [DX4047]
CAT24C01@TSOT-23 [DX1041]
CAT24C01@TSSOP8 [DX1059]
CAT24C01B(J)@SOIC8 [DX1045]
CAT24C01B(L) [DX0001]
CAT24C01B(P) [DX0001]
CAT24C01B(R)@MSOP8 [DX1059]
CAT24C01B(U)@TSSOP8 [DX1059]
CAT24C01B(W)@SOIC8 [DX1045]
CAT24C01B(Y)@TSSOP8 [DX1059]
CAT24C01B(Z)@MSOP8 [DX1059]
CAT24C02 [DX0001]
CAT24C02@MSOP8 [DX1015]
CAT24C02@SOIC14 [DX1030]
CAT24C02@SOIC8 [DX1045]
CAT24C02@TDFN8 [DX4047]
CAT24C02@TSOT-23 [DX1041]
CAT24C02@TSSOP8 [DX1059]
CAT24C021 [DX0001]
CAT24C022 [DX0001]
CAT24C023 [DX0001]
CAT24C03 [DX0001]
CAT24C03@SOIC8 [DX1045]
CAT24C03@TDFN8 [DX4047]
CAT24C03@TSSOP8 [DX1059]
CAT24C04 [DX0001]
CAT24C04@MSOP8 [DX1015]
CAT24C04@SOIC14 [DX1030]
CAT24C04@SOIC8 [DX1045]
CAT24C04@TDFN8 [DX4047]
CAT24C04@TSOT-23 [DX1041]
CAT24C04@TSSOP8 [DX1059]
CAT24C041 [DX0001]
CAT24C042 [DX0001]
CAT24C043 [DX0001]
CAT24C05 [DX0001]
CAT24C05@SOIC8 [DX1045]
CAT24C05@TDFN8 [DX4047]
CAT24C05@TSSOP8 [DX1059]
CAT24C08 [DX0001]
CAT24C08@MSOP8 [DX1015]
CAT24C08@SOIC14 [DX1030]
CAT24C08@SOIC8 [DX1045]
CAT24C08@TDFN8 [DX4047]
CAT24C08@TSOT-23 [DX1041]
CAT24C08@TSSOP8 [DX1059]
CAT24C081 [DX0001]
CAT24C082 [DX0001]
CAT24C083 [DX0001]
CAT24C08I [DX0001]
CAT24C08I@SOIC8 [DX1045]
CAT24C09 [DX0001]
CAT24C09@SOIC8 [DX1045]
CAT24C09@TDFN8 [DX4047]
CAT24C09@TSSOP8 [DX1059]
CAT24C128 [DX0001]
CAT24C128@SOIC8 [DX1045]
CAT24C128@TSSOP8 [DX1059]
CAT24C128@UDFN8 [DX4047]
CAT24C16 [DX0001]
CAT24C16@SOIC14 [DX1030]
CAT24C16@SOIC8 [DX1045]
CAT24C16@TDFN8 [DX4047]
CAT24C16@TSSOP8 [DX1059]
CAT24C161 [DX0001]
CAT24C162 [DX0001]
CAT24C163 [DX0001]
CAT24C164 [DX0001]
CAT24C164@SOIC8 [DX1045]
CAT24C164@TSSOP8 [DX1059]
CAT24C16I [DX0001]
CAT24C16I@SOIC8 [DX1045]
CAT24C208(J)@SOIC8 [DX1045]
CAT24C208(L) [DX0001]
CAT24C208(P) [DX0001]
CAT24C208(R)@MSOP8 [DX1015]

CAT24C208(U)@TSSOP8 [DX1059]
CAT24C208(W)@SOIC8 [DX1045]
CAT24C208(Y)@TSSOP8 [DX1059]
CAT24C208(Z)@MSOP8 [DX1015]
CAT24C21 [DX0001]
CAT24C21@SOIC8 [DX1045]
CAT24C21@TSSOP8 [DX1059]
CAT24C256 [DX0001]
CAT24C256@SOIC8 [DX1045]
CAT24C32 [DX0001]
CAT24C32@SOIC8 [DX1045]
CAT24C32@UDFN8 [DX4047]
CAT24C44 [DX0001]
CAT24C44@SOIC8 [DX1045]
CAT24C64 [DX0001]
CAT24C64@SOIC8 [DX1045]
CAT24C64@TSSOP8 [DX1059]
CAT24F32 [DX0001]
CAT24F32@SOIC8 [DX1045]
CAT24F32@TSSOP8 [DX1059]
CAT24F32A [DX0001]
CAT24F32A@SOIC8 [DX1045]
CAT24F32A@TSSOP8 [DX1059]
CAT24FC01 [DX0001]
CAT24FC01@SOIC14 [DX1030]
CAT24FC01@SOIC8 [DX1045]
CAT24FC01@TDFN8 [DX4047]
CAT24FC01@TSSOP8 [DX1059]
CAT24FC02 [DX0001]
CAT24FC02@SOIC14 [DX1030]
CAT24FC02@SOIC8 [DX1045]
CAT24FC02@TDFN8 [DX4047]
CAT24FC02@TSSOP8 [DX1059]
CAT24FC16 [DX0001]
CAT24FC16@SOIC14 [DX1030]
CAT24FC16@SOIC8 [DX1045]
CAT24FC16@TDFN8 [DX4047]
CAT24FC16@TSSOP8 [DX1059]
CAT24FC17 [DX0001]
CAT24FC17@SOIC8 [DX1045]
CAT24FC17@TDFN8 [DX4047]
CAT24FC17@TSSOP8 [DX1059]
CAT24FC256 [DX0001]
CAT24FC256@SOIC8 [DX1045]
CAT24FC256@TDFN8 [DX4005]
CAT24FC256@TSSOP8 [DX1059]
CAT24FC32 [DX0001]
CAT24FC32@SOIC8 [DX1045]
CAT24FC32@TDFN8 [DX4005]
CAT24FC32@TSSOP8 [DX1059]
CAT24FC64 [DX0001]
CAT24FC64@SOIC8 [DX1045]
CAT24FC64@TDFN8 [DX4005]
CAT24FC64@TSSOP8 [DX1059]
CAT24FC65 [DX0001]
CAT24FC65@SOIC8 [DX1045]
CAT24FC65@TDFN8 [DX4005]
CAT24FC65@TSSOP8 [DX1059]
CAT24FC66 [DX0001]
CAT24FC66@SOIC8 [DX1045]
CAT24FC66@TDFN8 [DX4005]
CAT24FC66@TSSOP8 [DX1059]
CAT24LC02 [DX0001]
CAT24LC02@SOIC8 [DX1045]
CAT24LC02@TDFN8 [DX4047]
CAT24LC02@TSSOP8 [DX1059]
CAT24WC01 [DX0001]
CAT24WC01@SOIC8 [DX1045]
CAT24WC01@TSSOP8 [DX1059]
CAT24WC02 [DX0001]
CAT24WC02@SOIC8 [DX1045]
CAT24WC02@TSSOP8 [DX1059]
CAT24WC03 [DX0001]
CAT24WC03@SOIC8 [DX1045]
CAT24WC03@TSSOP8 [DX1059]
CAT24WC04 [DX0001]
CAT24WC04@SOIC8 [DX1045]
CAT24WC04@TSSOP8 [DX1059]
CAT24WC05 [DX0001]
CAT24WC05@SOIC8 [DX1045]
CAT24WC05@TSSOP8 [DX1059]
CAT24WC08 [DX0001]
CAT24WC08@SOIC8 [DX1045]
CAT24WC08@TSSOP8 [DX1059]
CAT24WC09 [DX0001]
CAT24WC09@SOIC8 [DX1045]
CAT24WC09@TSSOP8 [DX1059]
CAT24WC128 [DX0001]
CAT24WC128@SOIC8 [DX1045]
CAT24WC128@TSSOP8 [DX1059]
CAT24WC129 [DX0001]
CAT24WC129@SOIC8 [DX1045]
CAT24WC16 [DX0001]
CAT24WC16@SOIC8 [DX1045]
CAT24WC16@TSSOP8 [DX1059]
CAT24WC164 [DX0001]

CAT24WC164@SOIC8 [DX1045]
CAT24WC164@TSSOP8 [DX1059]
CAT24WC17 [DX0001]
CAT24WC17@SOIC8 [DX1045]
CAT24WC17@TSSOP8 [DX1059]
CAT24WC256 [DX0001]
CAT24WC256@SOIC8 [DX1045]
CAT24WC257 [DX0001]
CAT24WC257@SOIC8 [DX1045]
CAT24WC32 [DX0001]
CAT24WC32@SOIC8 [DX1045]
CAT24WC33 [DX0001]
CAT24WC33@SOIC8 [DX1045]
CAT24WC64 [DX0001]
CAT24WC64@SOIC8 [DX1045]
CAT24WC64@TSSOP8 [DX1059]
CAT24WC65 [DX0001]
CAT24WC65@SOIC8 [DX1045]
CAT24WC66 [DX0001]
CAT24WC66@SOIC8 [DX1045]
CAT25010 [DX0001]
CAT25010(S)@SOIC8 [DX1044]
CAT25010(U)@TSSOP8 [DX1045]
CAT25020 [DX0001]
CAT25020(S)@SOIC8 [DX1044]
CAT25020(U)@TSSOP8 [DX1045]
CAT25040 [DX0001]
CAT25040(S)@SOIC8 [DX1044]
CAT25040(U)@TSSOP8 [DX1045]
CAT25080 [DX0001]
CAT25080@SOIC8 [DX1045]
CAT25080@TDFN8 [DX4002]
CAT25080@TSSOP8 [DX1059]
CAT25080@UDFN8 [DX0001]
CAT25128 [DX0001]
CAT25128@SOIC8 [DX1045]
CAT25128@TDFN8 [DX4002]
CAT25128@TSSOP8 [DX1059]
CAT25160 [DX0001]
CAT25160@SOIC8 [DX1045]
CAT25160@TDFN8 [DX4002]
CAT25160@TSSOP8 [DX1059]
CAT25160@UDFN8 [DX0001]
CAT25256 [DX0001]
CAT25256@SOIC8 [DX1045]
CAT25256@TDFN8 [DX4002]
CAT25256@TSSOP8 [DX1059]
CAT25320 [DX0001]
CAT25320@SOIC8 [DX1045]
CAT25320@TDFN8 [DX4002]
CAT25320@TSSOP8 [DX1059]
CAT25640 [DX0001]
CAT25640@SOIC8 [DX1045]
CAT25640@TDFN8 [DX4002]
CAT25640@TSSOP8 [DX1059]
CAT25C01 [DX0001]
CAT25C01@SOIC16 [DX1016]
CAT25C01@SOIC8 [DX1045]
CAT25C01@TSSOP14 [DX1059]
CAT25C01@TSSOP8 [DX1059]
CAT25C02 [DX0001]
CAT25C02@SOIC16 [DX1016]
CAT25C02@SOIC8 [DX1045]
CAT25C02@TSSOP14 [DX1000]
CAT25C02@TSSOP8 [DX1059]
CAT25C03 [DX0001]
CAT25C03@SOIC8 [DX1045]
CAT25C03@TSSOP14 [DX1000]
CAT25C03@TSSOP8 [DX1059]
CAT25C04 [DX0001]
CAT25C04@SOIC16 [DX1016]
CAT25C04@SOIC8 [DX1045]
CAT25C04@TSSOP14 [DX1000]
CAT25C04@TSSOP8 [DX1059]
CAT25C05 [DX0001]
CAT25C05@SOIC8 [DX1045]
CAT25C05@TSSOP14 [DX1000]
CAT25C05@TSSOP8 [DX1059]
CAT25C08 [DX0001]
CAT25C08@SOIC16 [DX1016]
CAT25C08@SOIC8 [DX1045#1]
CAT25C08@TSSOP14 [DX1000]
CAT25C08@TSSOP8 [DX1059#1]
CAT25C09 [DX0001]
CAT25C09@SOIC8 [DX1045#1]
CAT25C09@TSSOP14 [DX1000]
CAT25C09@TSSOP8 [DX1059#1]
CAT25C11 [DX0001]
CAT25C11@SOIC8 [DX1045]
CAT25C11@TSSOP14 [DX1000]
CAT25C11@TSSOP8 [DX1059]
CAT25C128 [DX0001]
CAT25C128@SOIC16 [DX1016]
CAT25C128@SOIC8[150 mil] [DX1045#1]

CAT25C128@SOIC8[208 mil] [DX1044]

CAT25C128@TSSOP14 [DX1000]	CAT25C128@TSSOP20 [DX1000]
CAT25C16 [DX0001]	CAT25C16@SOIC16 [DX1016]
CAT25C16@SOIC8 [DX1045#1]	CAT25C16@TSSOP14 [DX1000]
CAT25C16@TSSOP8 [DX1059#1]	CAT25C17 [DX0001]
CAT25C17@SOIC8 [DX1045#1]	CAT25C17@TSSOP14 [DX1000]
CAT25C17@TSSOP8 [DX1059#1]	CAT25C256 [DX0001]

CAT25C256@SOIC16 [DX1016]

CAT25C256@SOIC8[150 mil] [DX1045#1]

CAT25C256@SOIC8[208 mil] [DX1044]

CAT25C256@TSSOP14 [DX1000]	CAT25C256@TSSOP20 [DX1000]
CAT25C32 [DX0001]	CAT25C32@SOIC8 [DX1045#1]
CAT25C32@TSSOP14 [DX1000]	CAT25C32@TSSOP20 [DX1000]
CAT25C33 [DX0001]	CAT25C33@SOIC8 [DX1045#1]
CAT25C33@TSSOP14 [DX1000]	CAT25C64 [DX0001]
CAT25C64@SOIC8 [DX1045#1]	CAT25C64@TSSOP14 [DX1000]
CAT25C64@TSSOP20 [DX1000]	CAT25C65 [DX0001]
CAT25C65@SOIC8 [DX1045#1]	CAT25C65@TSSOP14 [DX1000]
CAT27010 [DX0001]	CAT27010@PLCC32 [DX2032]
CAT27010@TSOP32 [DX1002]	CAT27128A [DX0001]
CAT27256 [DX0001]	CAT27512 [DX0001]
CAT27512@PLCC32 [DX2032]	CAT2764A [DX0001]
CAT27C16A [DX0001]	CAT27C210 [DX0001]
CAT27C210@PLCC44 [DX2044]	CAT27HC256 [DX0001]
CAT27HC256@PLCC32 [DX2032]	CAT27HC256I [DX0001]
CAT27HC256I@PLCC32 [DX2032]	CAT28C16A [DX0001]
CAT28C16A@PLCC32 [DX2032]	CAT28C16A@SOIC24 [DX1033]
CAT28C16AI [DX0001]	CAT28C16AI@PLCC32 [DX2032]
CAT28C16AI@SOIC24 [DX1033]	CAT28C17A [DX0001]
CAT28C17A@PLCC32 [DX2032]	CAT28C17AI [DX0001]
CAT28C17AI@PLCC32 [DX2032]	CAT28C256 [DX0001]
CAT28C256@PLCC32 [DX2032]	CAT28C256@TSOP28 [DX1024]
CAT28C256I [DX0001]	CAT28C256I@PLCC32 [DX2032]
CAT28C256I@TSOP28 [DX1024]	CAT28C257 [DX0001]
CAT28C257@PLCC32 [DX2032]	CAT28C257@TSOP28 [DX1024]
CAT28C512 [DX0001]	CAT28C512@PLCC32 [DX2032]
CAT28C512@TSOP32 [DX1002]	CAT28C512@TSOP40 [DX1006]
CAT28C513@PLCC32 [DX2032]	CAT28C64A [DX0001]
CAT28C64A@PLCC32 [DX2032]	CAT28C64A@SOIC28 [DX1033]
CAT28C64AI [DX0001]	CAT28C64AI@PLCC32 [DX2032]
CAT28C64AI@SOIC28 [DX1033]	CAT28C64B [DX0001]
CAT28C64B@PLCC32 [DX2032]	CAT28C64B@SOIC28 [DX1033]
CAT28C64B@TSOP28 [DX1024]	CAT28C64BI [DX0001]
CAT28C64BI@PLCC32 [DX2032]	CAT28C64BI@TSOP28 [DX1024]
CAT28C65B [DX0001]	CAT28C65B@PLCC32 [DX2032]
CAT28C65B@TSOP28 [DX1024]	CAT28C65BI [DX0001]
CAT28C65BI@PLCC32 [DX2032]	CAT28C65BI@TSOP28 [DX1024]
CAT28F001N-B@PLCC32 [DX2032]	CAT28F001N-T@PLCC32 [DX2032]

CAT28F001P-B [DX0001]
CAT28F001P-T [DX0001]
CAT28F001T-B@TSOP32 [DX1002]
CAT28F001T-T@TSOP32 [DX1002]
CAT28F002B [DX0001]
CAT28F002B@TSOP40 [DX1006]
CAT28F002T [DX0001]
CAT28F002T@TSOP40 [DX1006]
CAT28F010 [DX0001]
CAT28F010(REVERSE)@TSOP32 [DX1002]
CAT28F010@PLCC32 [DX2032]
CAT28F010@TSOP32 [DX1002]
CAT28F010I [DX0001]
CAT28F010I(REVERSE)@TSOP32 [DX1002]
CAT28F010I@PLCC32 [DX2032]
CAT28F010I@TSOP32 [DX1002]
CAT28F020 [DX0001]
CAT28F020(REVERSE)@TSOP32 [DX1002]
CAT28F020@PLCC32 [DX2032]
CAT28F020@TSOP32 [DX1002]
CAT28F020I [DX0001]
CAT28F020I(REVERSE)@TSOP32 [DX1002]
CAT28F020I@PLCC32 [DX2032]
CAT28F020I@TSOP32 [DX1002]
CAT28F102 [DX0001]
CAT28F102@PLCC44 [DX2044]
CAT28F102@TSOP40 [DX1005]
CAT28F512 [DX0001]
CAT28F512(REVERSE)@TSOP32 [DX1002]
CAT28F512@PLCC32 [DX2032]
CAT28F512@TSOP32 [DX1002]
CAT28F512I [DX0001]
CAT28F512I(REVERSE)@TSOP32 [DX1002]
CAT28F512I@PLCC32 [DX2032]
CAT28F512I@TSOP32 [DX1002]
CAT28LV256 [DX0001]
CAT28LV256@PLCC32 [DX2032]
CAT28LV256@TSOP28 [DX1024]
CAT28LV64 [DX0001]
CAT28LV64@PLCC32 [DX2032]
CAT28LV64@TSOP28 [DX1024]
CAT28LV65 [DX0001]
CAT28LV65@PLCC32 [DX2032]
CAT28LV65@TSOP28 [DX1024]
CAT33C101(08bit) [DX0001]
CAT33C101(08bit)@SOIC8 [DX1045]
CAT33C101(16bit) [DX0001]
CAT33C101(16bit)@SOIC8 [DX1045]
CAT33C101H(08bit) [DX0001]
CAT33C101H(08bit)@SOIC8 [DX1045]
CAT33C101H(16bit) [DX0001]
CAT33C101H(16bit)@SOIC8 [DX1045]
CAT33C101I(08bit) [DX0001]
CAT33C101I(08bit)@SOIC8 [DX1045]
CAT33C101I(16bit) [DX0001]
CAT33C101I(16bit)@SOIC8 [DX1045]
CAT33C104(08bit) [DX0001]
CAT33C104(08bit)@SOIC8 [DX1045]
CAT33C104(16bit) [DX0001]
CAT33C104(16bit)@SOIC8 [DX1045]
CAT33C104I(08bit) [DX0001]
CAT33C104I(08bit)@SOIC8 [DX1045]
CAT33C104I(16bit) [DX0001]
CAT33C104I(16bit)@SOIC8 [DX1045]
CAT34AC02 [DX0001]
CAT34AC02@SOIC8 [DX1045]
CAT34AC02@TSSOP8 [DX1059]
CAT34C02 [DX0001]
CAT34C02@SOIC8 [DX1045]
CAT34C02@TDFN8 [DX4047]
CAT34C02@TSSOP8 [DX1059]
CAT34FC02 [DX0001]
CAT34FC02@SOIC8 [DX1045]
CAT34FC02@TDFN8 [DX4047]
CAT34FC02@TSSOP8 [DX1059]
CAT34RC02 [DX0001]
CAT34RC02@SOIC8 [DX1045]
CAT34RC02@TDFN8 [DX4047]
CAT34RC02@TSSOP8 [DX1059]
CAT34TS02@TDFN8 [DX4047]
CAT34WC02 [DX0001]
CAT34WC02@SOIC8 [DX1045]
CAT34WC02@TDFN8 [DX4047]
CAT34WC02@TSSOP8 [DX1059]
CAT35C102 [DX0001]

CAT35C102H [DX0001]
CAT35C102I [DX0001]
CAT35C104(08bit) [DX0001]
CAT35C104(08bit)@SOIC8 [DX1045]
CAT35C104(16bit) [DX0001]
CAT35C104(16bit)@SOIC8 [DX1045]
CAT35C104H(08bit) [DX0001]
CAT35C104H(08bit)@SOIC8 [DX1045]
CAT35C104I(08bit) [DX0001]
CAT35C104I(08bit)@SOIC8 [DX1045]
CAT35C104I(16bit) [DX0001]
CAT35C104I(16bit)@SOIC8 [DX1045]
CAT59C11 [DX0001]
CAT59C11@SOIC8 [DX1045]
CAT59C11A [DX0001]
CAT59C11A@SOIC8 [DX1045]
CAT59C11H [DX0001]
CAT59C11H@SOIC8 [DX1045]
CAT59C11I [DX0001]
CAT59C11I@SOIC8 [DX1045]
CAT64LC10(J)@SOIC8 [DX1045]
CAT64LC10(P) [DX0001]
CAT64LC10(S)@SOIC8 [DX1045]
CAT64LC10(U)@TSSOP8 [DX1059]
CAT64LC10(UR)@TSSOP8 [DX1059]
CAT64LC20(J)@SOIC8 [DX1045]
CAT64LC20(P) [DX0001]
CAT64LC20(S)@SOIC8 [DX1045]
CAT64LC20(U)@TSSOP8 [DX1000]
CAT64LC20(UR)@TSSOP8 [DX1000]
CAT64LC40(J)@SOIC8 [DX1045]
CAT64LC40(P) [DX0001]
CAT64LC40(S)@SOIC8 [DX1045]
CAT64LC40(U)@TSSOP8 [DX1000]
CAT64LC40(UR)@TSSOP8 [DX1000]
CAT93C46(08bit) [DX0001]
CAT93C46(08bit)(J)@SOIC8 [DX1045]
CAT93C46(08bit)(K)@SOIC8 [DX1044]
CAT93C46(08bit)(S)@SOIC8 [DX1045]
CAT93C46(08bit)(U)@TSSOP8 [DX1059]
CAT93C46(16bit) [DX0001]
CAT93C46(16bit)(J)@SOIC8 [DX1045]
CAT93C46(16bit)(K)@SOIC8 [DX1044]
CAT93C46(16bit)(S)@SOIC8 [DX1045]
CAT93C46(16bit)(U)@TSSOP8 [DX1059]
CAT93C46A [DX0001]
CAT93C46R(08bit) [DX0001]
CAT93C46R(08bit)(V)@SOIC8 [DX1045]
CAT93C46R(08bit)(VP2)@TDFN8 [DX4002]
CAT93C46R(08bit)(W)@SOIC8 [DX1045]
CAT93C46R(08bit)(X)@SOIC8 [DX1045]
CAT93C46R(08bit)(Y)@TSSOP8 [DX1059]
CAT93C46R(16bit)(V)@SOIC8 [DX1045]
CAT93C46R(16bit)(VP2)@TDFN8 [DX4002]
CAT93C46R(16bit)(W)@SOIC8 [DX1045]
CAT93C46R(16bit)(X)@SOIC8 [DX1045]
CAT93C46R(16bit)(Y)@TSSOP8 [DX1059]
CAT93C46R-16 [DX0001]
CAT93C56(08bit) [DX0001]
CAT93C56(08bit)@SOIC8 [DX1045]
CAT93C56(08bit)@SSOP8 [DX1044]
CAT93C56(08bit)@TDFN8 [DX4002]
CAT93C56(08bit)@TSSOP8 [DX1059]
CAT93C56(08bit)@UDFN8 [DX4003]
CAT93C56(16bit) [DX0001]
CAT93C56(16bit)@SOIC8 [DX1045]
CAT93C56A [DX0001]
CAT93C57 [DX0001]
CAT93C66(08bit) [DX0001]
CAT93C66(08bit)@SOIC8 [DX1045]
CAT93C66(08bit)@TSSOP8 [DX1059]
CAT93C66(16bit) [DX0001]
CAT93C66(16bit)@SOIC8 [DX1045]
CAT93C66(16bit)@TSSOP8 [DX1059]
CAT93C66A [DX0001]
CAT93C76(08bit) [DX0001]

CAT93C76(08bit)(J)@SOIC8 [DX1045]
CAT93C76(08bit)(K)@SOIC8 [DX1044]
CAT93C76(08bit)(S)@SOIC8 [DX1045]
CAT93C76(08bit)(U)@TSSOP8 [DX1059]
CAT93C76(16bit) [DX0001]
CAT93C76(16bit)(J)@SOIC8 [DX1045]
CAT93C76(16bit)(K)@SOIC8 [DX1044]
CAT93C76(16bit)(S)@SOIC8 [DX1045]
CAT93C76(16bit)(U)@TSSOP8 [DX1059]
CAT93C86(08bit) [DX0001]
CAT93C86(08bit)(J)@SOIC8 [DX1045]
CAT93C86(08bit)(K)@SOIC8 [DX1044]
CAT93C86(08bit)(S)@SOIC8 [DX1045]
CAT93C86(08bit)(U)@TSSOP8 [DX1059]
CAT93C86(16bit) [DX0001]
CAT93C86(16bit)(J)@SOIC8 [DX1045]
CAT93C86(16bit)(K)@SOIC8 [DX1044]
CAT93C86(16bit)(S)@SOIC8 [DX1045]
CAT93C86(16bit)(U)@TSSOP8 [DX1059]
CAT93H46(08bit) [DX0001]
CAT93H46(08bit)(J)@SOIC8 [DX1045]
CAT93H46(08bit)(K)@SOIC8 [DX1044]
CAT93H46(08bit)(S)@SOIC8 [DX1045]
CAT93H46(08bit)(U)@TSSOP8 [DX1059]
CAT93H46(16bit) [DX0001]
CAT93H46(16bit)(J)@SOIC8 [DX1045]
CAT93H46(16bit)(K)@SOIC8 [DX1044]
CAT93H46(16bit)(S)@SOIC8 [DX1045]
CAT93H46(16bit)(U)@TSSOP8 [DX1059]
CAT93HC46(08bit) [DX0001]
CAT93HC46(08bit)(J)@SOIC8 [DX1045]
CAT93HC46(08bit)(K)@SOIC8 [DX1044]
CAT93HC46(08bit)(S)@SOIC8 [DX1045]
CAT93HC46(08bit)(U)@TSSOP8 [DX1059]
CAT93HC46(16bit) [DX0001]
CAT93HC46(16bit)(J)@SOIC8 [DX1045]
CAT93HC46(16bit)(K)@SOIC8 [DX1044]
CAT93HC46(16bit)(S)@SOIC8 [DX1045]
CAT93HC46(16bit)(U)@TSSOP8 [DX1059]

DRAM & SRAM

CAT71C256 [DX0001]
CAT71C256L [DX0001]
CAT71C256@TSOP28 [DX1001]
CAT71C256L@TSOP28 [DX1001]

CBC Microelectronics

E(E)PROM/FRAM/NVRAM

MC24LC02 [DX0001]
MC24LC02@SOP8 [DX1045]
MC24LC02@TSSOP8 [DX1059]
MC24LC04 [DX0001]
MC24LC04@SOP8 [DX1045]
MC24LC04@TSSOP8 [DX1059]
MC24LC08 [DX0001]
MC24LC08@SOP8 [DX1045]
MC24LC08@TSSOP8 [DX1059]
MC24LC16 [DX0001]
MC24LC16@SOP8 [DX1045]
MC24LC16@TSSOP8 [DX1059]

CERAMATE

E(E)PROM/FRAM/NVRAM

24LC02 [DX0001]
24LC02@SOIC8 [DX1045]
24LC02@TSSOP8 [DX1059]
24LC08 [DX0001]
24LC08@SOIC8 [DX1045]
24LC08@TSSOP8 [DX1059]
24LC16 [DX0001]
24LC16@SOIC8 [DX1045]
24LC16@TSSOP8 [DX1059]
24LLC02 [DX0001]
24LLC02@SOIC8 [DX1045]
24LLC02@TSSOP8 [DX1059]
24LLC08 [DX0001]
24LLC08@SOIC8 [DX1045]
24LLC08@TSSOP8 [DX1059]
93LC46 [DX0001]
93LC46@SOIC8 [DX1045]
93LC46R [DX0001]
93LC46R@SOIC8 [DX1045]
93LC56 [DX0001]
93LC56@SOIC8 [DX1045]
93LC66 [DX0001]
93LC66@SOIC8 [DX1045]

CETC58

PLD

JGAL16V8B [DX0001]
JGAL20V8B [DX0001]
JGAL22V10D [DX0001]

CFEON

E(E)PROM/FRAM/NVRAM

EN25F16 [DX0001]
EN25F16@SOP16 [DX1033#1]
EN25F16@SOP8 [DX1044#1]
EN25F16@VDFN8 [DX4005#1]
EN25F80 [DX0001]
EN25F80@SOP8 [DX1044#1]
EN25F80@VDFN8 [DX4005#1]
EN25Q128@BGA24 [DX5146]
EN25Q128@SOP16 [DX1072#1]
EN25Q128@VDFN8 [DX4006#1]
EN25QA128-B24 [DX5146]
EN25QA128-S16 [DX1033#1]
EN25QA128-S8 [DX1044#1]
EN25QA256@BGA24 [DX5146]
EN25QA32 [DX0001]
EN25QA32@SOP8 [DX1044#1]

EN25QA32@VDFN8 [DX4005#1]
EN25QA64-B24 [DX5146]
EN25QA64-S8 [DX1044#1]
EN25QH16 [DX0001]
EN25QH16@SOP8(150 mil) [DX1045#1]
EN25QH16@SOP8(200 mil) [DX1044#1]
EN25QH16@TFBGA24 [DX5146]
EN25QH16@VDFN8 [DX4006#1]
EN25QH256@SOP16 [DX1072#1]
EN25QH256@TFBGA24 [DX5146]
EN25QH256@VDFN8 [DX4006#1]
EN25QH32 [DX0001]
EN25QH32@SOP8 [DX1044#1]
EN25QH32@TFBGA24 [DX5146]
EN25QH32@VDFN8 [DX4005#1]
EN25QH32A [DX0001]
EN25QH32A@SOP8 [DX1044#1]
EN25QH32A@TFBGA24 [DX5146]
EN25QH32A@VDFN8 [DX4005#1]
EN25QH64 [DX0001]
EN25QH64@SOP8 [DX1044#1]
EN25QH64@TFBGA24 [DX5146]
EN25QH64@VDFN8 [DX4005#1]
EN25T16@SOP8 [DX1044#1]
EN25T16@VDFN8 [DX4005#1]
EN25T80 [DX0001]
EN25T80@SOP8 [DX1044#1]
EN25T80@VDFN8 [DX4005#1]
EN27SN1G08@BGA63 [DX5046-1]
EN29F002AB [DX0001]
EN29F002AB@PLCC32 [DX2032]
EN29F002AB@TSOP32 [DX1002]
EN29F002ANB [DX0001]
EN29F002ANB@PLCC32 [DX2032]
EN29F002ANB@TSOP32 [DX1002]
EN29F002ANT [DX0001]
EN29F002ANT@PLCC32 [DX2032]
EN29F002ANT@TSOP32 [DX1002]
EN29F002AT [DX0001]
EN29F002AT@PLCC32 [DX2032]
EN29F002AT@TSOP32 [DX1002]
EN29F002B [DX0001]
EN29F002B@PLCC32 [DX2032]
EN29F002B@TSOP32 [DX1002]
EN29F002NB [DX0001]
EN29F002NB@PLCC32 [DX2032]
EN29F002NB@TSOP32 [DX1002]
EN29F002NT [DX0001]
EN29F002NT@PLCC32 [DX2032]
EN29F002NT@TSOP32 [DX1002]
EN29F002T [DX0001]
EN29F002T@PLCC32 [DX2032]
EN29F002T@TSOP32 [DX1002]
EN29F010 [DX0001]
EN29F010@PLCC32 [DX2032]
EN29F010@TSOP32 [DX1002]
EN29F010@VSOP32 [DX1003]
EN29F040 [DX0001]
EN29F040@PLCC32 [DX2032]
EN29F040@TSOP32 [DX1002]
EN29F040A [DX0001]
EN29F040A@PLCC32 [DX2032]
EN29F040A@TSOP32 [DX1002]
EN29F080@TSOP40 [DX1006]
EN29F512 [DX0001]
EN29F512@PLCC32 [DX2032]
EN29F512@TSOP32 [DX1002]
EN29F512@VSOP32 [DX1003]
EN29F800B@TSOP48 [DX1004]
EN29F800T@TSOP48 [DX1004]
EN29GA128H@FBGA64 [DX5074]
EN29GA128L@FBGA64 [DX5074]
EN29GA256H@FBGA64 [DX5074]
EN29GA256L@FBGA64 [DX5074]
EN29GL064AB@FBGA48 [DX5002]
EN29GL064AB@TSOP48 [DX1004]
EN29GL064AT@FBGA48 [DX5002]
EN29GL064AT@TSOP48 [DX1004]
EN29GL064B@FBGA48 [DX5002]
EN29GL064B@TSOP48 [DX1004]
EN29GL064H@FBGA64 [DX5074]
EN29GL064H@TSOP56 [DX1011]
EN29GL064L@FBGA64 [DX5074]
EN29GL064L@TSOP56 [DX1011]
EN29GL064T@FBGA48 [DX5002]
EN29GL064T@TSOP48 [DX1004]
EN29GL128H@FBGA64 [DX5074]
EN29GL128H@TSOP56 [DX1011]
EN29GL128L@FBGA64 [DX5074]
EN29GL128L@TSOP56 [DX1011]
EN29LV010@PLCC32 [DX2032]
EN29LV010@TSOP32 [DX1002]
EN29LV010@VSOP32 [DX1003]
EN29LV010@WFBGA34 [DX5037]

EN29LV040@PLCC32 [DX2032]
EN29LV040@TSOP32 [DX1002]
EN29LV040@VSOP32 [DX1003]
EN29LV040A [DX0001]
EN29LV040A@PLCC32 [DX2032]
EN29LV040A@TSOP32 [DX1002]
EN29LV040A@VSOP32 [DX1003]
EN29LV160AB@FBGA48 [DX5002]
EN29LV160AB@TSOP48 [DX1004]
EN29LV160AT@FBGA48 [DX5002]
EN29LV160AT@TSOP48 [DX1004]
EN29LV160B@FBGA48 [DX5002]
EN29LV160B@TSOP48 [DX1004]
EN29LV160BB@FBGA48 [DX5002]
EN29LV160BB@TSOP48 [DX1004]
EN29LV160BT@FBGA48 [DX5002]
EN29LV160BT@TSOP48 [DX1004]
EN29LV160CB@FBGA48 [DX5002]
EN29LV160CB@TSOP48 [DX1004]
EN29LV160CT@FBGA48 [DX5002]
EN29LV160T@FBGA48 [DX5002]
EN29LV160T@TSOP48 [DX1004]
EN29LV160TB@TSOP48 [DX1004]
EN29LV320AB@FBGA48 [DX5002]
EN29LV320AB@TSOP48 [DX1004]
EN29LV320AT@FBGA48 [DX5002]
EN29LV320AT@TSOP48 [DX1004]
EN29LV320B@FBGA48 [DX5002]
EN29LV320B@TSOP48 [DX1004]
EN29LV320BB@FBGA48 [DX5002]
EN29LV320BB@TSOP48 [DX1004]
EN29LV320BT@FBGA48 [DX5002]
EN29LV320BT@TSOP48 [DX1004]
EN29LV320CB@FBGA48 [DX5002]
EN29LV320CB@TSOP48 [DX1004]
EN29LV320CT@FBGA48 [DX5002]
EN29LV320CT@TSOP48 [DX1004]
EN29LV320T@FBGA48 [DX5002]
EN29LV320T@TSOP48 [DX1004]
EN29LV400AB@FBGA48 [DX5002]
EN29LV400AB@TSOP48 [DX1004]
EN29LV400AT@FBGA48 [DX5002]
EN29LV400AT@TSOP48 [DX1004]
EN29LV400B@FBGA48 [DX5002]
EN29LV400B@TSOP48 [DX1004]
EN29LV400T@FBGA48 [DX5002]
EN29LV400T@TSOP48 [DX1004]
EN29LV512@PLCC32 [DX2032]
EN29LV512@TSOP32 [DX1002]
EN29LV512@VSOP32 [DX1003]
EN29LV640AB@FBGA48 [DX5002]
EN29LV640AB@TSOP48 [DX1004]
EN29LV640AT@FBGA48 [DX5002]
EN29LV640AT@TSOP48 [DX1004]
EN29LV640B@FBGA48 [DX5002]
EN29LV640B@TSOP48 [DX1004]
EN29LV640H@FBGA48 [DX5002]
EN29LV640H@TSOP48 [DX1004]
EN29LV640L@FBGA48 [DX5002]
EN29LV640L@TSOP48 [DX1004]
EN29LV640T@FBGA48 [DX5002]
EN29LV640T@TSOP48 [DX1004]
EN29LV641H@FBGA63 [DX5041]
EN29LV641H@TSOP48 [DX1004]
EN29LV641L@FBGA63 [DX5041]
EN29LV641L@TSOP48 [DX1004]
EN29LV800AB@FBGA48 [DX5002]
EN29LV800AB@TSOP48 [DX1004]
EN29LV800AT@FBGA48 [DX5002]
EN29LV800AT@TSOP48 [DX1004]
EN29LV800B@TSOP48 [DX1004]
EN29LV800BB@FBGA48 [DX5002]
EN29LV800BB@TSOP48 [DX1004]
EN29LV800BT@FBGA48 [DX5002]
EN29LV800BT@TSOP48 [DX1004]
EN29LV800CB@FBGA48 [DX5002]
EN29LV800CB@TSOP48 [DX1004]
EN29LV800CT@FBGA48 [DX5002]
EN29LV800CT@TSOP48 [DX1004]
EN29LV800T@TSOP48 [DX1004]
EN29NS064@FBGA56 [DX5094]
EN29PL032@FBGA48 [DX5002]
EN29PL032@FBGA56 [DX5045]
EN29PL032@TSOP48 [DX1004]
EN29PL032A@TSOP48 [DX1004]
EN29PL064@FBGA48 [DX5002]
EN29PL064@FBGA56 [DX5045]
EN29PL064@TSOP48 [DX1004]
EN29SL160B@FBGA48 [DX5002]
EN29SL160B@TSOP48 [DX1004]
EN29SL160B@WFBGA48 [DX5038]
EN29SL160B@WLGA48 [DX5038]
EN29SL160T@FBGA48 [DX5002]
EN29SL160T@TSOP48 [DX1004]
EN29SL160T@WFBGA48 [DX5038]
EN29SL160T@WLGA48 [DX5038]

EN29SL400B@FBGA48 [DX5002]
EN29SL400B@TSOP48 [DX1004]
EN29SL400T@FBGA48 [DX5002]
EN29SL400T@TSOP48 [DX1004]
EN29SL800B@FBGA48 [DX5002]
EN29SL800B@TSOP48 [DX1004]
EN29SL800B@WFBGA48 [DX5038]
EN29SL800B@WLGA48 [DX5038]
EN29SL800T@FBGA48 [DX5002]
EN29SL800T@TSOP48 [DX1004]
EN29SL800T@WFBGA48 [DX5038]
EN29SL800T@WLGA48 [DX5038]
EN39LV010@PLCC32 [DX2032]
EN39LV010@VSOP32 [DX1003]
EN39LV010@WFBGA34 [DX5037]
EN39SL160H@FBGA48 [DX5002]
EN39SL160H@WFBGA48 [DX5037]
EN39SL160L@FBGA48 [DX5002]
EN39SL160L@WFBGA48 [DX5037]
EN39SL800@FBGA48 [DX5002]
EN39SL800@TSOP48 [DX1043]
EN39SL800@WFBGA48 [DX5037]
EN39SL801@FBGA48 [DX5002]
EN39SL801@WFBGA48 [DX5037]
EN71GL03280@FBGA56 [DX5045]
EN71GL032A0@FBGA56 [DX5045]
EN71GL064B0@FBGA56 [DX5045]
EN71GL128B0@FBGA56 [DX5045]
EN71NS032A0@FBGA56 [DX5094]
EN71NS064B0@FBGA56 [DX5094]
EN71NS128B0@FBGA56 [DX5094]
EN71NS128C0@FBGA56 [DX5094]
EN71PL03280@FBGA56 [DX5045]
EN71PL032A0@FBGA56 [DX5045]
EN71PL032A0A@FBGA56 [DX5045]
EN71PL064A0@FBGA56 [DX5045]
EN71PL064B0@FBGA56 [DX5045]
EN71SN10E-45CFWP@BGA107 [DX5028]
EN71SN10E-45EBWP@BGA130 [DX5140-1]
EN71SN10F-45EBWP@BGA130 [DX5140-1]

CHEMTRONICS

MICROCONTROLLER

CT1C08@MLF24 [DX4012]
CT1C08S@MLF24 [DX4012]

CHIGO

MICROCONTROLLER

MN103SFJ9D [DX3003]
MN103SFJ9DXW [DX3003]

CHINA CORE

MICROCONTROLLER

CCM89C51 [DX0001]
CCM89C51@PLCC44 [DX2044]
CCM89C51@TQFP44 [DX3003]
CCM89C52 [DX0001]
CCM89C52@PLCC44 [DX2044]
CCM89C52@TQFP44 [DX3003]

CHINGIS

E(E)PROM/FRAM/NVRAM

PM25LD010@SOP8 [DX1045#1]
PM25LD010@TSSOP8 [DX1059#3]
PM25LD010@WSON8 [DX4005#1]
PM25LD010C@SOP8 [DX1045#1]
PM25LD010C@SOP8(SG) [DX1045#1]
PM25LD010C@TSSOP8 [DX1059#3]
PM25LD010C@TSSOP8(SG) [DX1059#1]
PM25LD010C@WSON8 [DX4005#1]
PM25LD010C@WSON8(SG) [DX4005#1]
PM25LD020@SOP8 [DX1045#1]
PM25LD020@TSSOP8 [DX1059#3]
PM25LD020@WSON8 [DX4005#1]
PM25LD020C@SOP8 [DX1045#1]
PM25LD020C@SOP8(SG) [DX1045#1]
PM25LD020C@TSSOP8 [DX1059#3]
PM25LD020C@TSSOP8(SG) [DX1059#1]
PM25LD020C@WSON8 [DX4005#1]
PM25LD020C@WSON8(SG) [DX4005#1]
PM25LD040(B)@SOIC8 [DX1044#1]
PM25LD040(Q)@WSON8 [DX4005#1]
PM25LD040(S)@SOIC8 [DX1045#1]
PM25LD256C@SOP8 [DX1045#1]
PM25LD256C@TSSOP8 [DX1059#3]
PM25LD256C@WSON8 [DX4005#1]
PM25LD512@SOP8 [DX1045#1]
PM25LD512@TSSOP8 [DX1059#3]
PM25LD512@WSON8 [DX4005#1]
PM25LD512C@SOP8 [DX1045#1]
PM25LD512C@TSSOP8 [DX1059#3]
PM25LD512C@WSON8 [DX4005#1]
PM25LV010(B)@SOIC8 [DX1044]
PM25LV010(Q)@WSON8 [DX4005]
PM25LV010(S)@SOIC8 [DX1045]
PM25LV020(B)@SOIC8 [DX1044#1]
PM25LV020(Q)@WSON8 [DX4005#1]
PM25LV020(S)@SOIC8 [DX1045#1]
PM25LV040(B)@SOIC8 [DX1044#1]
PM25LV040(Q)@WSON8 [DX4005#1]
PM25LV040(S)@SOIC8 [DX1045#1]
PM25LV512(B)@SOIC8 [DX1044]
PM25LV512(Q)@WSON8 [DX4005]
PM25LV512(S)@SOIC8 [DX1045]
PM25W020(B)@SOIC8 [DX1044#1]
PM25W020(Q)@WSON8 [DX4005#1]
PM25W020(S)@SOIC8 [DX1045#1]
PM29F002B [DX0001]
PM29F002B@PLCC32 [DX2032]
PM29F002T [DX0001]
PM29F002T@PLCC32 [DX2032]
PM29F004B [DX0001]
PM29F004B@PLCC32 [DX2032]
PM29F004T [DX0001]
PM29F004T@PLCC32 [DX2032]
PM29LV002B [DX0001]
PM29LV002B@PLCC32 [DX2032]
PM29LV002B@VSOP32 [DX1003]
PM29LV002T [DX0001]
PM29LV002T@PLCC32 [DX2032]
PM29LV002T@VSOP32 [DX1003]
PM29LV004B@PLCC32 [DX2032]
PM29LV004B@VSOP32 [DX1003]
PM29LV004T@PLCC32 [DX2032]
PM29LV004T@VSOP32 [DX1003]
PM29LV104RB@PLCC32 [DX2032]
PM29LV104RB@VSOP32 [DX1003]
PM29LV104RT@PLCC32 [DX2032]
PM29LV104RT@VSOP32 [DX1003]
PM37LV512 [DX0001]
PM37LV512@PLCC32 [DX2032]
PM37LV512@VSOP32 [DX1003]
PM39F010 [DX0001]
PM39F010@PLCC32 [DX2032]
PM39F010@VSOP32 [DX1003]
PM39F020 [DX0001]
PM39F020@PLCC32 [DX2032]
PM39F020@VSOP32 [DX1003]
PM39F040 [DX0001]
PM39F040@PLCC32 [DX2032]
PM39F040@VSOP32 [DX1003]
PM39LV010@PLCC32 [DX2032]
PM39LV010@VSOP32 [DX1003]
PM39LV010R@PLCC32 [DX2032]
PM39LV010R@VSOP32 [DX1003]
PM39LV020@PLCC32 [DX2032]
PM39LV020@VSOP32 [DX1003]
PM39LV040@PLCC32 [DX2032]
PM39LV040@VSOP32 [DX1003]
PM39LV512@PLCC32 [DX2032]
PM39LV512@VSOP32 [DX1003]
PM39LV512R@PLCC32 [DX2032]
PM39LV512R@VSOP32 [DX1003]
PM49FL002T@PLCC32 [DX2032]
PM49FL002T@VSOP32 [DX1003]
PM49FL004T@PLCC32 [DX2032]

PM49FL004T@VSOP32 [DX1003]
PM49FL008T@VSOP32 [DX1003]
PM49LP002T@VSOP32 [DX1003]
PM49FL008T@PLCC32 [DX2032]
PM49LP002T@PLCC32 [DX2032]

CHIPCON

MICROCONTROLLER

CC1010@TQFP64 [DX3011]
CC1110F16@QLP36 [DX4021]
CC2430F128@QLP48 [DX4021]
CC2430F64@QLP48 [DX4021]
CC2431F32@QLP48 [DX4021]
CC2510F08@QLP36 [DX4021]
CC2510F32@QLP36 [DX4021]
CC2511F16@QLP36 [DX4021]
CC1110F08@QLP36 [DX4021]
CC1110F32@QLP36 [DX4021]
CC2430F32@QLP48 [DX4021]
CC2431F128@QLP48 [DX4021]
CC2431F64@QLP48 [DX4021]
CC2510F16@QLP36 [DX4021]
CC2511F08@QLP36 [DX4021]
CC2511F32@QLP36 [DX4021]

CHIPMAST

MICROCONTROLLER

M151-S1@SOP16 [DX1016]
M152-S2@SOP16 [DX1016]
M151-S2@SOP16 [DX1016]

CHIPON

MICROCONTROLLER

C61F120 [DX0001]
C61F120@SOIC8 [DX1032]
C61F121 [DX0001]
C61F121@TSSOP14 [DX1000]
C61F132@QFN8 [DX4005]
C61F132@SSOP20 [DX1026]
C61F133 [DX0001]
C61F133@TSSOP14 [DX1000]
C61F182@QFN28 [DX4014]
C61F182@SSOP28 [DX1026]
C61F183@QFN28 [DX4014]
C61F183@SSOP28 [DX1026]
C61F184@QFN44 [DX4018]
C61F186 [DX0001]
C61F186@SOIC28 [DX1033]
C61F187 [DX0001]
C61F187@QFP44 [DX3003]
C61F120@QFN8 [DX4005]
C61F120@SSOP8 [DX1016]
C61F121@SOIC14 [DX1030]
C61F132 [DX0001]
C61F132@SOIC8 [DX1032]
C61F132@SSOP8 [DX1016]
C61F133@SOIC14 [DX1030]
C61F182 [DX0001]
C61F182@SOIC28 [DX1033]
C61F183 [DX0001]
C61F183@SOIC28 [DX1033]
C61F184 [DX0001]
C61F184@QFP44 [DX3003]
C61F186@QFN28 [DX4014]
C61F186@SSOP28 [DX1026]
C61F187@QFN44 [DX4018]
C61F21 [DX0001]

C61F21@QFN8 [DX4004]
C61F21@SOIC8 [DX1032]
C61F21@SSOP8 [DX1016]
C61F23 [DX0001]
C61F23@QFN16 [DX4010]
C61F23@SOIC14 [DX1030]
C61F23@TSSOP14 [DX1000]

CHIPONE

MICROCONTROLLER

ICN1137@QFN28 [DX4036]
ICN1218@QFN40 [DX4017]
ICN1314@QFN32 [DX4015]

CHIPSEA

MICROCONTROLLER

CSU824 [DX0001]
CSU824S [DX1033]

CHIPSIP

E(E)PROM/FRAM/NVRAM

CT48248NS246C1@FBGA119 [DX5184]
CT48248NS486C1@FBGA119 [DX5184]
CT4824H11246C1@FBGA119 [DX5184]
M5E1G8126AB@BGA107 [DX5028]

CHIPSWINNER

E(E)PROM/FRAM/NVRAM

CW24C02 [DX0001]
CW24C02@DFN8 [DX4047]
CW24C02@SOP8 [DX1045]
CW24C02@SOT23-5 [DX1041]
CW24C02@TSOT23-5 [DX1041]
CW24C02@TSSOP8 [DX1059]
CW24C02B [DX0001]
CW24C02B@DFN8 [DX4047]
CW24C02B@SOP8 [DX1045]
CW24C02B@SOT23-5 [DX1041]
CW24C02B@TSOT23-5 [DX1041]
CW24C02B@TSSOP8 [DX1059]
CW24C02C [DX0001]
CW24C02C@DFN8 [DX4047]
CW24C02C@SOP8 [DX1045]
CW24C02C@SOT23-5 [DX1041]
CW24C02C@TSOT23-5 [DX1041]
CW24C02C@TSSOP8 [DX1059]
CW24C04 [DX0001]
CW24C04@DFN8 [DX4047]
CW24C04@SOP8 [DX1045]
CW24C04@SOT23-5 [DX1041]
CW24C04@TSOT23-5 [DX1041]
CW24C04@TSSOP8 [DX1059]
CW24C04A [DX0001]
CW24C04A@DFN8 [DX4047]
CW24C04A@SOP8 [DX1045]
CW24C04A@SOT23-5 [DX1041]
CW24C04A@TSOT23-5 [DX1041]
CW24C04A@TSSOP8 [DX1059]
CW24C08 [DX0001]
CW24C08@DFN8 [DX4047]

CW24C08@SOP8 [DX1045]
CW24C08@SOT23-5 [DX1041]
CW24C08@TSOT23-5 [DX1041]
CW24C08@TSSOP8 [DX1059]
CW24C08B [DX0001]
CW24C08B@DFN8 [DX4047]
CW24C08B@SOP8 [DX1045]
CW24C08B@SOT23-5 [DX1041]
CW24C08B@TSOT23-5 [DX1041]
CW24C08B@TSSOP8 [DX1059]
CW24C08C [DX0001]
CW24C08C@DFN8 [DX4047]
CW24C08C@SOP8 [DX1045]
CW24C08C@SOT23-5 [DX1041]
CW24C08C@TSOT23-5 [DX1041]
CW24C08C@TSSOP8 [DX1059]
CW24C128 [DX0001]
CW24C128@DFN8 [DX4047]
CW24C128@SOP8 [DX1045]
CW24C128@TSSOP8 [DX1059]
CW24C16 [DX0001]
CW24C16@DFN8 [DX4047]
CW24C16@SOP8 [DX1045]
CW24C16@SOT23-5 [DX1041]
CW24C16@TSOT23-5 [DX1041]
CW24C16@TSSOP8 [DX1059]
CW24C16A [DX0001]
CW24C16A@DFN8 [DX4047]
CW24C16A@SOP8 [DX1045]
CW24C16A@SOT23-5 [DX1041]
CW24C16A@TSOT23-5 [DX1041]
CW24C16A@TSSOP8 [DX1059]
CW24C256 [DX0001]
CW24C256@DFN8 [DX4047]
CW24C256@SOP8 [DX1045]
CW24C256@TSSOP8 [DX1059]
CW24C32 [DX0001]
CW24C32@DFN8 [DX4047]
CW24C32@SOP8 [DX1045]
CW24C32@TSSOP8 [DX1059]
CW24C64 [DX0001]
CW24C64@DFN8 [DX4047]
CW24C64@SOP8 [DX1045]
CW24C64@TSSOP8 [DX1059]
CW25P01@SOP8 [DX1045]
CW25P02@SOP8 [DX1045]
CW25P05@SOP8 [DX1045]
CW25P10@SOP8 [DX1045]

MICROCONTROLLER

CW89F51 [DX0001]
CW89F51@PLCC44 [DX2044]
CW89F51@TQFP44 [DX3002]
CW89F52 [DX0001]
CW89F52@PLCC44 [DX2044]
CW89F52@TQFP44 [DX3002]
CW89F54 [DX0001]
CW89F54@PLCC44 [DX2044]
CW89F54@TQFP44 [DX3002]

CHK

MICROCONTROLLER

HEA08F20A@SOIC20 [DX1033]

CHRONTEL

MICROCONTROLLER

CH9904 [DX1045]

CKD Technology

E(E)PROM/FRAM/NVRAM

CKD24A02 [DX0001]
CKD24A02@SOP8 [DX1045]

CORERIVER

E(E)PROM/FRAM/NVRAM

CR24C01 [DX0001]
CR24C01@SOIC8 [DX1045]
CR24C01@TDFN8 [DX4047]
CR24C01@TSSOP8 [DX1059]
CR24C02 [DX0001]
CR24C02@SOIC8 [DX1045]
CR24C02@TDFN8 [DX4047]
CR24C02@TSSOP8 [DX1059]
CR24C04 [DX0001]
CR24C04@SOIC8 [DX1045]
CR24C04@TDFN8 [DX4047]
CR24C04@TSSOP8 [DX1059]
CR24C08 [DX0001]
CR24C08@SOIC8 [DX1045]
CR24C08@TDFN8 [DX4047]
CR24C08@TSSOP8 [DX1059]
CR24C128 [DX0001]
CR24C128@SOIC8 [DX1045]
CR24C128@TSSOP8 [DX1059]
CR24C16 [DX0001]
CR24C16@SOIC8 [DX1045]
CR24C16@TDFN8 [DX4047]
CR24C16@TSSOP8 [DX1059]
CR24C256 [DX0001]
CR24C256@SOIC8 [DX1045]
CR24C256@TSSOP8 [DX1059]
CR24C32 [DX0001]
CR24C32@SOIC8 [DX1045]
CR24C32@TSSOP8 [DX1059]
CR24C64 [DX0001]
CR24C64@SOIC8 [DX1045]
CR24C64@TSSOP8 [DX1059]

MICROCONTROLLER

GC87C520A0 [DX0001]
GC87C520A0@MQFP44 [DX3002]
GC87C520A0@PLCC44 [DX2044]
GC89L541A0@LQFP44 [DX3002]
GC89L541A0@MLF32 [DX4015]
GC89L541A0@MQFP44 [DX3066]
GC89L541A0@PQFP44 [DX3066]
GC89L541A0@QFN32 [DX4015]
GC89L581A0@LQFP44 [DX3002]
GC89L581A0@MLF32 [DX4015]
GC89L581A0@MQFP44 [DX3066]
GC89L581A0@PQFP44 [DX3066]
GC89L581A0@QFN32 [DX4015]
GC89L591A0@LQFP44 [DX3002]
GC89L591A0@MLF32 [DX4015]
GC89L591A0@MQFP44 [DX3066]
GC89L591A0@PQFP44 [DX3066]
GC89L591A0@QFN32 [DX4015]
TouchCore32H@MLF24 [DX4012]

Customer

MICROCONTROLLER

Erase79F9211GB [DX3003]
Test79F9211GB [DX3003]

CW

E(E)PROM/FRAM/NVRAM

FM(4*S29GL128N) [DXG4P4]
FM(4*S29GL128N)(new) [DX1089]

CWI

E(E)PROM/FRAM/NVRAM

39LV040@VSOP32 [DX1003]

CYGNAL

MICROCONTROLLER

C8051F000@TQFP64 [DX3011]
C8051F001@TQFP48 [DX3007]
C8051F002@TQFP32 [DX3001]
C8051F005@TQFP64 [DX3011]
C8051F006@TQFP48 [DX3007]
C8051F007@TQFP32 [DX3001]
C8051F010@TQFP64 [DX3011]
C8051F011@TQFP48 [DX3007]
C8051F012@TQFP32 [DX3001]
C8051F015@TQFP64 [DX3011]
C8051F016@TQFP48 [DX3007]
C8051F017@TQFP32 [DX3001]
C8051F018@TQFP64
C8051F019@TQFP48
C8051F020@TQFP100 [DX3021]
C8051F020JTAG [DX0001]
C8051F021@TQFP64 [DX3011]
C8051F021JTAG [DX0001]
C8051F022@TQFP100 [DX3021]
C8051F022JTAG [DX0001]
C8051F023@TQFP64 [DX3011]
C8051F023JTAG [DX0001]
C8051F040@TQFP100 [DX3021]
C8051F040JTAG [DX0001]
C8051F041@TQFP64 [DX3011]
C8051F041JTAG [DX0001]
C8051F042@TQFP100 [DX3021]
C8051F042JTAG [DX0001]
C8051F043@TQFP64 [DX3011]
C8051F043JTAG [DX0001]
C8051F044@TQFP100 [DX3021]
C8051F044JTAG [DX0001]
C8051F045@TQFP64 [DX3011]
C8051F045JTAG [DX0001]
C8051F046@TQFP100 [DX3021]
C8051F046JTAG [DX0001]
C8051F047@TQFP64 [DX3011]
C8051F047JTAG [DX0001]
C8051F060@TQFP100 [DX3021]
C8051F061@TQFP64 [DX3011]
C8051F062@TQFP100 [DX3021]
C8051F063@TQFP64 [DX3011]
C8051F064@TQFP100 [DX3021]
C8051F065@TQFP64 [DX3011]
C8051F066@TQFP100 [DX3021]
C8051F067@TQFP64 [DX3011]
C8051F120*ISP [DX0001]
C8051F120@TQFP100 [DX3021]
C8051F120-GQ*ISP [DX0001]
C8051F120-GQ@TQFP100 [DX3021]
C8051F121*ISP [DX0001]
C8051F121@TQFP64 [DX3011]
C8051F121-GQ*ISP [DX0001]
C8051F121-GQ@TQFP64 [DX3011]
C8051F122*ISP [DX0001]
C8051F122@TQFP100 [DX3021]
C8051F122-GQ*ISP [DX0001]
C8051F122-GQ@TQFP100 [DX3021]

C8051F123*ISP [DX0001]
C8051F123-GQ*ISP [DX0001]
C8051F124*ISP [DX0001]
C8051F124-GQ*ISP [DX0001]
C8051F125*ISP [DX0001]
C8051F125-GQ*ISP [DX0001]
C8051F126*ISP [DX0001]
C8051F126-GQ*ISP [DX0001]
C8051F127*ISP [DX0001]
C8051F127-GQ*ISP [DX0001]
C8051F130*ISP [DX0001]
C8051F130-GQ*ISP [DX0001]
C8051F131*ISP [DX0001]
C8051F131-GQ*ISP [DX0001]
C8051F132*ISP [DX0001]
C8051F132-GQ*ISP [DX0001]
C8051F133*ISP [DX0001]
C8051F133-GQ*ISP [DX0001]
C8051F206@TQFP48 [DX3007]
C8051F221@TQFP32 [DX3001]
C8051F230@TQFP48 [DX3007]
C8051F236@TQFP48 [DX3007]
C8051F300-GM@QFN11 [DX4007]
C8051F301@QFN11 [DX4007]
C8051F301-GS [DX1016]
C8051F302-GM@QFN11 [DX4007]
C8051F303@QFN11 [DX4007]
C8051F303-GS [DX1016]
C8051F304-GM@QFN11 [DX4007]
C8051F305@QFN11 [DX4007]
C8051F305-GS [DX1016]
C8051F310A@TQFP32 [DX3001]
C8051F310-GQ@TQFP32 [DX3001]
C8051F311-GM@QFN28 [DX4013]
C8051F312-GQ@TQFP32 [DX3001]
C8051F313-GM@QFN28 [DX4013]
C8051F314-GQ@TQFP32 [DX3001]
C8051F315-GM@QFN28 [DX4013]
C8051F317-GM@QFN24 [DX4012]
C8051F320A@TQFP32 [DX3001]
C8051F320-GQ@TQFP32 [DX3001]
C8051F321@QFN28(Left Down) [DX4013]
C8051F321A@QFN28 [DX4013]
C8051F321A@QFN28(Left Down) [DX4013]
C8051F321A-GM@QFN28 [DX4013]
C8051F321A-GM@QFN28(Left Down) [DX4013]
C8051F321-GM@QFN28 [DX4013]
C8051F321-GM@QFN28(Left Down) [DX4013]
C8051F123@TQFP64 [DX3011]
C8051F123-GQ@TQFP64 [DX3011]
C8051F124@TQFP100 [DX3021]
C8051F124-GQ@TQFP100 [DX3021]
C8051F125@TQFP64 [DX3011]
C8051F125-GQ@TQFP64 [DX3011]
C8051F126@TQFP100 [DX3021]
C8051F126-GQ@TQFP100 [DX3021]
C8051F127@TQFP64 [DX3011]
C8051F127-GQ@TQFP64 [DX3011]
C8051F130@TQFP100 [DX3021]
C8051F130-GQ@TQFP100 [DX3021]
C8051F131@TQFP64 [DX3011]
C8051F131-GQ@TQFP64 [DX3011]
C8051F132@TQFP100 [DX3021]
C8051F132-GQ@TQFP100 [DX3021]
C8051F133@TQFP64 [DX3011]
C8051F133-GQ@TQFP64 [DX3011]
C8051F220@TQFP48 [DX3007]
C8051F226@TQFP48 [DX3007]
C8051F231@TQFP32 [DX3001]
C8051F300@QFN11 [DX4007]
C8051F300-GS [DX1016]
C8051F301-GM@QFN11 [DX4007]
C8051F302@QFN11 [DX4007]
C8051F302-GS [DX1016]
C8051F303-GM@QFN11 [DX4007]
C8051F304@QFN11 [DX4007]
C8051F304-GS [DX1016]
C8051F305-GM@QFN11 [DX4007]
C8051F310@TQFP32 [DX3001]
C8051F310A-GQ@TQFP32 [DX3001]
C8051F311@QFN28 [DX4013]
C8051F312@TQFP32 [DX3001]
C8051F313@QFN28 [DX4013]
C8051F314@TQFP32 [DX3001]
C8051F315@QFN28 [DX4013]
C8051F316-GM@QFN24 [DX4012]
C8051F320@TQFP32 [DX3001]
C8051F320A-GQ@TQFP32 [DX3001]
C8051F321@QFN28 [DX4013]

C8051F326@QFN28 [DX4013]
C8051F326-GM@QFN28 [DX4013]
C8051F326-GQ@QFN28 [DX4013]
C8051F327@QFN28 [DX4013]
C8051F327-GM@QFN28 [DX4013]
C8051F327-GQ@QFN28 [DX4013]
C8051F330@MLP20 [DX4011]
C8051F330D [DX0001]
C8051F330-GM@MLP20 [DX4011]
C8051F330-GP [DX0001]
C8051F331@MLP20 [DX4011]
C8051F331-GM@MLP20 [DX4011]
C8051F332@MLP20 [DX4011]
C8051F332-GM@MLP20 [DX4011]
C8051F333@MLP20 [DX4011]
C8051F333-GM@MLP20 [DX4011]
C8051F334@MLP20 [DX4011]
C8051F334-GM@MLP20 [DX4011]
C8051F335@MLP20 [DX4011]
C8051F335-GM@MLP20 [DX4011]
C8051F336@MLP20 [DX4011]
C8051F336-GM@MLP20 [DX4011]
C8051F337@MLP20 [DX4011]
C8051F337-GM@MLP20 [DX4011]
C8051F338@MLP24 [DX4012]
C8051F338-GM@MLP24 [DX4012]
C8051F339@MLP24 [DX4012]
C8051F339-GM@MLP24 [DX4012]
C8051F340@TQFP48 [DX3007]
C8051F340-GQ@TQFP48 [DX3007]
C8051F341@TQFP48 [DX3007]
C8051F341-GQ@TQFP48 [DX3007]
C8051F342@LQFP32 [DX3001]
C8051F342-GQ@LQFP32 [DX3001]
C8051F343@LQFP32 [DX3001]
C8051F343-GQ@LQFP32 [DX3001]
C8051F344@TQFP48 [DX3007]
C8051F344-GQ@TQFP48 [DX3007]
C8051F345@TQFP48 [DX3007]
C8051F345-GQ@TQFP48 [DX3007]
C8051F346@LQFP32 [DX3001]
C8051F346-GQ@LQFP32 [DX3001]
C8051F347@LQFP32 [DX3001]
C8051F347-GQ@LQFP32 [DX3001]
C8051F348@TQFP48 [DX3007]
C8051F348-GQ@TQFP48 [DX3007]
C8051F349@LQFP32 [DX3001]
C8051F349-GQ@LQFP32 [DX3001]
C8051F34A@LQFP32 [DX3001]
C8051F34A-GQ@LQFP32 [DX3001]
C8051F34B@LQFP32 [DX3001]
C8051F34B-GQ@LQFP32 [DX3001]
C8051F34C@TQFP48 [DX3007]
C8051F34D@LQFP32 [DX3001]
C8051F350-GQ@LQFP32 [DX3001]
C8051F351-GM@QFN28 [DX4013]
C8051F352-GQ@LQFP32 [DX3001]
C8051F353-GM@QFN28 [DX4013]
C8051F360@QFP48 [DX3007]
C8051F361@QFP32 [DX3001]
C8051F362@QFN28 [DX4013]
C8051F363@QFP48 [DX3007]
C8051F364@QFP32 [DX3001]
C8051F365@QFN28 [DX4013]
C8051F366@QFP32 [DX3001]
C8051F367@QFN28 [DX4013]
C8051F368@QFP32 [DX3001]
C8051F369@QFN28 [DX4013]
C8051F370-A-GM [DX4012]
C8051F370-GM [DX4012]
C8051F371-A-GM [DX4012]
C8051F371-GM [DX4012]
C8051F374-A-GM [DX4012]
C8051F374-GM [DX4012]
C8051F375-A-GM [DX4012]
C8051F375-GM [DX4012]
C8051F380@TQFP48 [DX3007]
C8051F381@QFN32 [DX4015]
C8051F381@TQFP32 [DX3001]
C8051F382@TQFP48 [DX3007]
C8051F383@QFN32 [DX4015]
C8051F383@TQFP32 [DX3001]
C8051F384@TQFP48 [DX3007]
C8051F385@QFN32 [DX4015]
C8051F385@TQFP32 [DX3001]
C8051F386@TQFP48 [DX3007]
C8051F387@QFN32 [DX4015]
C8051F387@TQFP32 [DX3001]
C8051F388-GQ [DX3007]
C8051F389-GM [DX4015]
C8051F389-GQ [DX3001]
C8051F38A-GQ [DX3007]
C8051F38B-GM [DX4015]
C8051F38B-GQ [DX3001]
C8051F390-A-GM [DX4012]
C8051F390-GM [DX4012]

C8051F391-A-GM [DX4012]	C8051F391-GM [DX4012]
C8051F392-A-GM [DX4011]	C8051F392-GM [DX4011]
C8051F393-A-GM [DX4011]	C8051F393-GM [DX4011]
C8051F394-A-GM [DX4012]	C8051F394-GM [DX4012]
C8051F395-A-GM [DX4012]	C8051F395-GM [DX4012]
C8051F396-A-GM [DX4011]	C8051F396-GM [DX4011]
C8051F397-A-GM [DX4011]	C8051F397-GM [DX4011]
C8051F398-A-GM [DX4011]	C8051F398-GM [DX4011]
C8051F399-A-GM [DX4011]	C8051F399-GM [DX4011]
C8051F410@LQFP32 [DX3001]	C8051F410-GQ@LQFP32 [DX3001]
C8051F411@QFN28 [DX4013]	C8051F411-GM@QFN28 [DX4013]
C8051F412@LQFP32 [DX3001]	C8051F412-GQ@LQFP32 [DX3001]
C8051F413@QFN28 [DX4013]	C8051F413-GM@QFN28 [DX4013]
C8051F500-IM@QFN48 [DX4021]	C8051F500-IQ@QFP48 [DX3007]
C8051F501-IM@QFN48 [DX4021]	C8051F501-IQ@QFP48 [DX3007]
C8051F502-IM@QFN32 [DX4015]	C8051F502-IQ@QFP32 [DX3001]
C8051F503-IM@QFN32 [DX4015]	C8051F503-IQ@QFP32 [DX3001]
C8051F504-IM@QFN48 [DX4021]	C8051F504-IQ@QFP48 [DX3007]
C8051F505-IM@QFN48 [DX4021]	C8051F505-IQ@QFP48 [DX3007]
C8051F506-IM@QFN32 [DX4015]	C8051F506-IQ@QFP32 [DX3001]
C8051F507-IM@QFN32 [DX4015]	C8051F507-IQ@QFP32 [DX3001]
C8051F508-IM@QFN40 [DX4017]	C8051F509-IM@QFN40 [DX4017]
C8051F510-IM@QFN40 [DX4017]	C8051F511-IM@QFN40 [DX4017]
C8051F520A-IM@QFN10 [DX4007]	C8051F520-IM@QFN10 [DX4007]
C8051F521A-IM@QFN10 [DX4007]	C8051F521-IM@QFN10 [DX4007]
C8051F523A-IM@QFN10 [DX4007]	C8051F523-IM@QFN10 [DX4007]
C8051F524A-IM@QFN10 [DX4007]	C8051F524-IM@QFN10 [DX4007]
C8051F526A-IM@QFN10 [DX4007]	C8051F526-IM@QFN10 [DX4007]
C8051F527A-IM@QFN10 [DX4007]	C8051F527-IM@QFN10 [DX4007]
C8051F530A-IM@QFN20 [DX4011]	C8051F530A-IT@TSSOP20 [DX1000]
C8051F530-IM@QFN20 [DX4011]	C8051F530-IT@TSSOP20 [DX1000]
C8051F531A-IM@QFN20 [DX4011]	C8051F531A-IT@TSSOP20 [DX1000]
C8051F531-IM@QFN20 [DX4011]	C8051F531-IT@TSSOP20 [DX1000]
C8051F533A-IM@QFN20 [DX4011]	C8051F533A-IT@TSSOP20 [DX1000]
C8051F533-IM@QFN20 [DX4011]	C8051F533-IT@TSSOP20 [DX1000]
C8051F534A-IM@QFN20 [DX4011]	C8051F534A-IT@TSSOP20 [DX1000]
C8051F534-IM@QFN20 [DX4011]	C8051F534-IT@TSSOP20 [DX1000]
C8051F536A-IM@QFN20 [DX4011]	C8051F536A-IT@TSSOP20 [DX1000]
C8051F536-IM@QFN20 [DX4011]	C8051F536-IT@TSSOP20 [DX1000]
C8051F537A-IM@QFN20 [DX4011]	C8051F537A-IT@TSSOP20 [DX1000]
C8051F537-IM@QFN20 [DX4011]	C8051F537-IT@TSSOP20 [DX1000]
C8051F540-IM@QFN32 [DX4015]	C8051F540-IQ@QFP32 [DX3001]
C8051F541-IM@QFN32 [DX4015]	C8051F541-IQ@QFP32 [DX3001]
C8051F542-IM@QFN24 [DX4012]	C8051F543-IM@QFN24 [DX4012]
C8051F544-IM@QFN32 [DX4015]	C8051F544-IQ@QFP32 [DX3001]
C8051F545-IM@QFN32 [DX4015]	C8051F545-IQ@QFP32 [DX3001]
C8051F546-IM@QFN24 [DX4012]	C8051F547-IM@QFN24 [DX4012]
C8051F550-IM@QFN24 [DX4012]	C8051F551-IM@QFN24 [DX4012]

C8051F552-IM@QFN24 [DX4012]
C8051F553-IM@QFN24 [DX4012]
C8051F554-IM@QFN24 [DX4012]
C8051F555-IM@QFN24 [DX4012]
C8051F556-IM@QFN24 [DX4012]
C8051F557-IM@QFN24 [DX4012]
C8051F560-IM@QFN32 [DX4015]
C8051F560-IQ@QFP32 [DX3001]
C8051F561-IM@QFN32 [DX4015]
C8051F561-IQ@QFP32 [DX3001]
C8051F562-IM@QFN32 [DX4015]
C8051F562-IQ@QFP32 [DX3001]
C8051F563-IM@QFN32 [DX4015]
C8051F563-IQ@QFP32 [DX3001]
C8051F564-IM@QFN32 [DX4015]
C8051F564-IQ@QFP32 [DX3001]
C8051F565-IM@QFN32 [DX4015]
C8051F565-IQ@QFP32 [DX3001]
C8051F566-IM@QFN32 [DX4015]
C8051F566-IQ@QFP32 [DX3001]
C8051F567-IM@QFN32 [DX4015]
C8051F567-IQ@QFP32 [DX3001]
C8051F568-IM@QFN40 [DX4017]
C8051F569-IM@QFN40 [DX4017]
C8051F570-IM@QFN40 [DX4017]
C8051F571-IM@QFN40 [DX4017]
C8051F572-IM@QFN40 [DX4017]
C8051F573-IM@QFN40 [DX4017]
C8051F574-IM@QFN40 [DX4017]
C8051F575-IM@QFN40 [DX4017]
C8051F580-AM@QFN48 [DX4021]
C8051F580-AQ@QFP48 [DX3047]
C8051F580-IM@QFN48 [DX4021]
C8051F580-IQ@QFP48 [DX3047]
C8051F581-AM@QFN48 [DX4021]
C8051F581-AQ@QFP48 [DX3047]
C8051F581-IM@QFN48 [DX4021]
C8051F581-IQ@QFP48 [DX3047]
C8051F582-AM@QFN32 [DX4015]
C8051F582-AQ@QFP32 [DX3001]
C8051F582-IM@QFN32 [DX4015]
C8051F582-IQ@QFP32 [DX3001]
C8051F583-AM@QFN32 [DX4015]
C8051F583-AQ@QFP32 [DX3001]
C8051F583-IM@QFN32 [DX4015]
C8051F583-IQ@QFP32 [DX3001]
C8051F584-AM@QFN48 [DX4021]
C8051F584-AQ@QFP48 [DX3047]
C8051F584-IM@QFN48 [DX4021]
C8051F584-IQ@QFP48 [DX3047]
C8051F585-AM@QFN48 [DX4021]
C8051F585-AQ@QFP48 [DX3047]
C8051F585-IM@QFN48 [DX4021]
C8051F585-IQ@QFP48 [DX3047]
C8051F586-AM@QFN32 [DX4015]
C8051F586-AQ@QFP32 [DX3001]
C8051F586-IM@QFN32 [DX4015]
C8051F586-IQ@QFP32 [DX3001]
C8051F587-AM@QFN32 [DX4015]
C8051F587-AQ@QFP32 [DX3001]
C8051F587-IM@QFN32 [DX4015]
C8051F587-IQ@QFP32 [DX3001]
C8051F588-AM@QFN40 [DX4017]
C8051F588-IM@QFN40 [DX4017]
C8051F589-AM@QFN40 [DX4017]
C8051F589-IM@QFN40 [DX4017]
C8051F590-AM@QFN40 [DX4017]
C8051F590-IM@QFN40 [DX4017]
C8051F591-AM@QFN40 [DX4017]
C8051F591-IM@QFN40 [DX4017]
C8051F700-GQ@QFP64 [DX3011]
C8051F701-GQ@QFP64 [DX3011]
C8051F702-GQ@QFP64 [DX3011]
C8051F703-GQ@QFP64 [DX3011]
C8051F704-GM@QFN48 [DX4021]
C8051F704-GQ@QFP48 [DX3047]
C8051F705-GM@QFN48 [DX4021]
C8051F705-GQ@QFP48 [DX3047]
C8051F706-GM@QFN48 [DX4021]
C8051F706-GQ@QFP48 [DX3047]
C8051F707-GM@QFN48 [DX4021]
C8051F707-GQ@QFP48 [DX3047]
C8051F708-GQ@QFP64 [DX3011]
C8051F709-GQ@QFP64 [DX3011]
C8051F710-GQ@QFP64 [DX3011]
C8051F711-GQ@QFP64 [DX3011]
C8051F712-GM@QFN48 [DX4021]
C8051F712-GQ@QFP48 [DX3047]
C8051F713-GM@QFN48 [DX4021]
C8051F713-GQ@QFP48 [DX3047]
C8051F714-GM@QFN48 [DX4021]
C8051F714-GQ@QFP48 [DX3047]
C8051F715-GM@QFN48 [DX4021]
C8051F715-GQ@QFP48 [DX3047]
C8051F716-GM [DX4015]
C8051F717-GM [DX4012]

C8051F750B-GM [DX4021]
C8051F750B-GM1 [DX4043]
C8051F750-GM [DX4021]
C8051F750-GM1 [DX4043]
C8051F751B-GM [DX4015]
C8051F751-GM [DX4015]
C8051F752B-GM [DX4012]
C8051F752-GM [DX4012]
C8051F755B-GM [DX4021]
C8051F755B-GM1 [DX4043]
C8051F755-GM [DX4021]
C8051F755-GM1 [DX4043]
C8051F756B-GM [DX4015]
C8051F756-GM [DX4015]
C8051F757B-GM [DX4012]
C8051F757-GM [DX4012]
C8051F760-GM [DX4021]
C8051F760-GM1 [DX4043]
C8051F761-GM [DX4015]
C8051F762-GM [DX4012]
C8051F765-GM [DX4021]
C8051F765-GM1 [DX4043]
C8051F766-GM [DX4015]
C8051F767-GM [DX4012]
C8051F800-GM@QFN20 [DX4011]
C8051F800-GU@QSOP24 [DX1001]
C8051F801-GM@QFN20 [DX4011]
C8051F801-GU@QSOP24 [DX1001]
C8051F802-GM@QFN20 [DX4011]
C8051F802-GU@QSOP24 [DX1001]
C8051F803-GS@SOIC16 [DX1016]
C8051F804-GS@SOIC16 [DX1016]
C8051F805-GS@SOIC16 [DX1016]
C8051F806-GM@QFN20 [DX4011]
C8051F806-GU@QSOP24 [DX1001]
C8051F807-GM@QFN20 [DX4011]
C8051F807-GU@QSOP24 [DX1001]
C8051F808-GM@QFN20 [DX4011]
C8051F808-GU@QSOP24 [DX1001]
C8051F809-GS@SOIC16 [DX1016]
C8051F810-GS@SOIC16 [DX1016]
C8051F811-GS@SOIC16 [DX1016]
C8051F812-GM@QFN20 [DX4011]
C8051F812-GU@QSOP24 [DX1001]
C8051F813-GM@QFN20 [DX4011]
C8051F813-GU@QSOP24 [DX1001]
C8051F814-GM@QFN20 [DX4011]
C8051F814-GU@QSOP24 [DX1001]
C8051F815-GS@SOIC16 [DX1016]
C8051F816-GS@SOIC16 [DX1016]
C8051F817-GS@SOIC16 [DX1016]
C8051F818-GM@QFN20 [DX4011]
C8051F818-GU@QSOP24 [DX1001]
C8051F819-GM@QFN20 [DX4011]
C8051F819-GU@QSOP24 [DX1001]
C8051F820-GM@QFN20 [DX4011]
C8051F820-GU@QSOP24 [DX1001]
C8051F821-GS@SOIC16 [DX1016]
C8051F822-GS@SOIC16 [DX1016]
C8051F823-GS@SOIC16 [DX1016]
C8051F824-GS@SOIC16 [DX1016]
C8051F825-GS@SOIC16 [DX1016]
C8051F826-GS@SOIC16 [DX1016]
C8051F827-GS@SOIC16 [DX1016]
C8051F828-GS@SOIC16 [DX1016]
C8051F829-GS@SOIC16 [DX1016]
C8051F830-GS@SOIC16 [DX1016]
C8051F831-GS@SOIC16 [DX1016]
C8051F832-GS@SOIC16 [DX1016]
C8051F833-GS@SOIC16 [DX1016]
C8051F834-GS@SOIC16 [DX1016]
C8051F835-GS@SOIC16 [DX1016]
C8051F850-C-GM [DX4038]
C8051F850-C-GU [DX1001]
C8051F851-C-GM [DX4038]
C8051F851-C-GU [DX1001]
C8051F852-C-GM [DX4038]
C8051F852-C-GU [DX1001]
C8051F853-C-GM [DX4038]
C8051F853-C-GU [DX1001]
C8051F854-C-GM [DX4038]
C8051F854-C-GU [DX1001]
C8051F855-C-GM [DX4038]
C8051F855-C-GU [DX1001]
C8051F860-C-GS [DX1016]
C8051F861-C-GS [DX1016]
C8051F862-C-GS [DX1016]
C8051F863-C-GS [DX1016]
C8051F864-C-GS [DX1016]
C8051F865-C-GS [DX1016]
C8051F901-GM@QFN24 [DX4012]
C8051F901-GU@QSOP24 [DX1001]
C8051F902-GM@QFN24 [DX4012]
C8051F902-GU@QSOP24 [DX1001]
C8051F911-GM@QFN24 [DX4012]
C8051F911-GU@QSOP24 [DX1001]

C8051F912-GM@QFN24 [DX4012]
C8051F912-GU@QSOP24 [DX1001]
C8051F920-F-GM@QFN32 [DX4015]
C8051F920-F-GQ@LQFP32 [DX3001]
C8051F920-GM@QFN32 [DX4015]
C8051F920-GQ@LQFP32 [DX3001]
C8051F921-F-GM@QFN24 [DX4012]
C8051F921-GM@QFN24 [DX4012]
C8051F930-F-GM@QFN32 [DX4015]
C8051F930-F-GQ@LQFP32 [DX3001]
C8051F930-GM@QFN32 [DX4015]
C8051F930-GQ@LQFP32 [DX3001]
C8051F931-F-GM@QFN24 [DX4012]
C8051F931-GM@QFN24 [DX4012]
C8051F960A-GM [DX0001]
C8051F960A-GQ [DX3016]
C8051F960-GM [DX0001]
C8051F960-GQ [DX3016]
C8051F961A-GM [DX4017]
C8051F961-GM [DX4017]
C8051F962A-GM [DX0001]
C8051F962A-GQ [DX3016]
C8051F962-GM [DX0001]
C8051F962-GQ [DX3016]
C8051F963A-GM [DX4017]
C8051F963-GM [DX4017]
C8051F964A-GM [DX0001]
C8051F964A-GQ [DX3016]
C8051F964-GM [DX0001]
C8051F964-GQ [DX3016]
C8051F965A-GM [DX4017]
C8051F965-GM [DX4017]
C8051F966A-GM [DX0001]
C8051F966A-GQ [DX3016]
C8051F966-GM [DX0001]
C8051F966-GQ [DX3016]
C8051F967A-GM [DX4017]
C8051F967-GM [DX4017]
C8051F968A-GM [DX0001]
C8051F968A-GQ [DX3016]
C8051F968-GM [DX0001]
C8051F968-GQ [DX3016]
C8051F969A-GM [DX4017]
C8051F969-GM [DX4017]
C8051F980-GM [DX4038]
C8051F981-GM [DX4038]
C8051F982-GM [DX4038]
C8051F983-GM [DX4038]
C8051F985-GM [DX4038]
C8051F986-GM [DX4012]
C8051F986-GU [DX1001]
C8051F987-GM [DX4012]
C8051F987-GU [DX1001]
C8051F988-GM [DX4012]
C8051F988-GU [DX1001]
C8051F989-GM [DX4012]
C8051F989-GU [DX1001]
C8051F990-GM [DX4038]
C8051F991-GM [DX4038]
C8051F996-GM [DX4012]
C8051F996-GU [DX1001]
C8051F997-GM [DX4012]
C8051F997-GU [DX1001]
C8051T320-B-GQ [DX3001]
C8051T320-GQ@LQFP32 [DX3001]
C8051T321-B-GM [DX4013]
C8051T321-GM@QFN28 [DX4013]
C8051T322-B-GQ [DX3001]
C8051T322-GQ@LQFP32 [DX3001]
C8051T323-B-GM [DX4013]
C8051T323-GM@QFN28 [DX4013]
C8051T326-B-GM [DX4013]
C8051T326-GM@QFN28 [DX4013]
C8051T327-B-GM [DX4013]
C8051T327-GM@QFN28 [DX4013]
C8051T600@QFN11 [DX4007]
C8051T600@TSSOP14 [DX1016]
C8051T601@QFN11 [DX4007]
C8051T601@TSSOP14 [DX1016]
C8051T602@QFN11 [DX4007]
C8051T602@TSSOP14 [DX1016]
C8051T603@QFN11 [DX4007]
C8051T603@TSSOP14 [DX1016]
C8051T604@QFN11 [DX4007]
C8051T604@TSSOP14 [DX1016]
C8051T605@QFN11 [DX4007]
C8051T605@TSSOP14 [DX1016]
C8051T606@MSOP10 [DX1016]
C8051T606@QFN10 [DX4035]
C8051T606@QFN11 [DX4007]
C8051T610-GQ@LQFP32 [DX3001]
C8051T610-GQ@LQFP32(old) [DX3001]
C8051T611-GM@QFN28 [DX4013]
C8051T611-GM@QFN28(old) [DX4013]

C8051T612-GQ@LQFP32 [DX3001]
C8051T612-GQ@LQFP32(old) [DX3001]
C8051T613-GM@QFN28 [DX4013]
C8051T613-GM@QFN28(old) [DX4013]
C8051T614-GQ@LQFP32 [DX3001]
C8051T614-GQ@LQFP32(old) [DX3001]
C8051T615-GM@QFN28 [DX4013]
C8051T615-GM@QFN28(old) [DX4013]
C8051T616-GM@QFN24 [DX4012]
C8051T616-GM@QFN24(old) [DX4012]
C8051T617-GM@QFN24 [DX4012]
C8051T617-GM@QFN24(old) [DX4012]
C8051T620-B-GM [DX4015]
C8051T620-GM@QFN32 [DX4015]
C8051T621-B-GM [DX4015]
C8051T621-GM@QFN32 [DX4015]
C8051T622-B-GM [DX4012]
C8051T622-GM@QFN24 [DX4012]
C8051T623-B-GM [DX4012]
C8051T623-GM@QFN24 [DX4012]
C8051T626-B-GM [DX4015]
C8051T627-B-GM [DX4015]
C8051T630@QFN20 [DX4011]
C8051T631@QFN20 [DX4011]
C8051T632@QFN20 [DX4011]
C8051T633@QFN20 [DX4011]
C8051T634@QFN20 [DX4011]
C8051T635@QFN20 [DX4011]
SI1000@QFN42(ISP) [DX0001]
SI1001@QFN42(ISP) [DX0001]
SI1002@QFN42(ISP) [DX0001]
SI1003@QFN42(ISP) [DX0001]
SI1004@QFN42(ISP) [DX0001]
SI1005@QFN42(ISP) [DX0001]
SI1010@QFN42(ISP) [DX0001]
SI1011@QFN42(ISP) [DX0001]
SI1012@QFN42(ISP) [DX0001]
SI1013@QFN42(ISP) [DX0001]
SI1014@QFN42(ISP) [DX0001]
SI1015@QFN42(ISP) [DX0001]
SI1020_A_GM(ISP) [DX0001]
SI1021_A_GM(ISP) [DX0001]
SI1022_A_GM(ISP) [DX0001]
SI1023_A_GM(ISP) [DX0001]
SI1024_A_GM(ISP) [DX0001]
SI1025_A_GM(ISP) [DX0001]
SI1026_A_GM(ISP) [DX0001]
SI1027_A_GM(ISP) [DX0001]
SI1030_A_GM(ISP) [DX0001]
SI1031_A_GM(ISP) [DX0001]
SI1032_A_GM(ISP) [DX0001]
SI1033_A_GM(ISP) [DX0001]
SI1034_A_GM(ISP) [DX0001]
SI1035_A_GM(ISP) [DX0001]
SI1036_A_GM(ISP) [DX0001]
SI1037_A_GM(ISP) [DX0001]
SI1060_A_GM(ISP) [DX0001]
SI1061_A_GM(ISP) [DX0001]
SI1062_A_GM(ISP) [DX0001]
SI1063_A_GM(ISP) [DX0001]
SI1064_A_GM(ISP) [DX0001]
SI1065_A_GM(ISP) [DX0001]
SI1080_A_GM(ISP) [DX0001]
SI1081_A_GM(ISP) [DX0001]
SI1082_A_GM(ISP) [DX0001]
SI1083_A_GM(ISP) [DX0001]
SI1084_A_GM(ISP) [DX0001]
SI1085_A_GM(ISP) [DX0001]
SI8250@LQFP32 [DX3001]
SI8250@QFN28 [DX4013]
SI8250-IM@QFN28 [DX4013]
SI8250-IQ@LQFP32 [DX3001]
SI8251@LQFP32 [DX3001]
SI8251@QFN28 [DX4013]
SI8251-IM@QFN28 [DX4013]
SI8251-IQ@LQFP32 [DX3001]
SI8252@LQFP32 [DX3001]
SI8252@QFN28 [DX4013]
SI8252-IM@QFN28 [DX4013]
SI8252-IQ@LQFP32 [DX3001]

CYPRESS

E(E)PROM/FRAM/NVRAM

CY14B101LA-SZ25X@SOIC32 [DX1069]
CY14B116N-Z30XI@TSOP48 [DX1004]
CY14B116N-Z45XI@TSOP48 [DX1004]
CY14B256KA-SP25X@TSOP48 [DX1028]
CY14B256LA-SZ45X@SOIC32 [DX1069]
CY14B256Q [DX0001]
CY14B256Q@SOIC16 [DX1016]
CY14B256Q@SOIC8 [DX1045]
CY14C256Q [DX0001]
CY14C256Q@SOIC16 [DX1016]
CY14C256Q@SOIC8 [DX1045]
CY14E116N-Z30XI@TSOP48 [DX1004]
CY14E256Q [DX0001]
CY14E256Q@SOIC16 [DX1016]
CY14E256Q@SOIC8 [DX1045]
CY27C010 [DX0001]
CY27C010@PLCC32 [DX2032]
CY27C010@TSOP32 [DX1002]
CY27C020 [DX0001]
CY27C020@PLCC32 [DX2032]
CY27C020@TSOP32 [DX1002]
CY27C040 [DX0001]
CY27C040@PLCC32 [DX2032]
CY27C040@TSOP32 [DX1002]
CY27C256 [DX0001]
CY27C256@PLCC32 [DX2032]
CY27C256@TSOP28 [DX1024]
CY27C512 [DX0001]
CY27C512@PLCC32 [DX2032]
CY27C512@TSOP28 [DX1024]
CY27H010 [DX0001]
CY27H010@PLCC32 [DX2032]
CY27H010@TSOP32 [DX1002]
CY27H256 [DX0001]
CY27H256@PLCC32 [DX2032]
CY27H256@TSOP28 [DX1024]
CY27H512 [DX0001]
CY27H512@PLCC32 [DX2032]
CY27H512@TSOP28 [DX1024]
CY7C1350G-200AXC@TQFP100 [DX3062]
CY7C1354C-166AXC@TQFP100 [DX3062]
CY7C1370D-200AXC@TQFP100 [DX3062]
CY7C225 [DX0001]
CY7C225@PLCC28 [DX2028]
CY7C225A [DX0001]
CY7C225A@PLCC28 [DX2028]
CY7C235 [DX0001]
CY7C235@PLCC28 [DX3028]
CY7C235A [DX0001]
CY7C235A@PLCC28 [DX3028]
CY7C243 [DX0001]
CY7C243@PLCC28 [DX3028]
CY7C244 [DX0001]
CY7C244@PLCC28 [DX3028]
CY7C245 [DX0001]
CY7C245@PLCC28 [DX3028]
CY7C245A [DX0001]
CY7C245A@PLCC28 [DX3028]
CY7C248@PLCC44 [DX2044]
CY7C249@PLCC44 [DX2044]
CY7C251 [DX0001]
CY7C251@PLCC32 [DX3032]
CY7C254 [DX0001]
CY7C254@PLCC32 [DX3032]
CY7C256 [DX0001]
CY7C256@PLCC32 [DX2032]
CY7C256A [DX0001]
CY7C256A@PLCC32 [DX2032]
CY7C258 [DX0001]
CY7C258@PLCC28 [DX2028]
CY7C259@PLCC44 [DX2044]
CY7C261 [DX0001]
CY7C261@PLCC28 [DX2028]
CY7C263 [DX0001]
CY7C263@PLCC28 [DX2028]
CY7C264 [DX0001]
CY7C264@PLCC28 [DX2028]
CY7C265 [DX0001]
CY7C265@PLCC28 [DX2028]
CY7C266 [DX0001]
CY7C266@PLCC32 [DX2032]
CY7C268 [DX0001]
CY7C268@PLCC32 [DX2032]
CY7C269 [DX0001]
CY7C269@PLCC28 [DX2028]
CY7C271 [DX0001]
CY7C271@PLCC32 [DX2032]
CY7C271A [DX0001]
CY7C271A@PLCC32 [DX2032]
CY7C274 [DX0001]
CY7C274@PLCC32 [DX2032]
CY7C276(25HC)@PLCC44 [DX2044]

CY7C276(25JC)@PLCC44 [DX2044]
CY7C276(30JC)@PLCC44 [DX2044]
CY7C281 [DX0001]
CY7C281@PLCC28 [DX3028]
CY7C281A [DX0001]
CY7C281A@PLCC28 [DX3028]
CY7C282 [DX0001]
CY7C282@PLCC28 [DX3028]
CY7C282A [DX0001]
CY7C282A@PLCC28 [DX3028]
CY7C285 [DX0001]
CY7C285@PLCC32 [DX3032]
CY7C286 [DX0001]
CY7C286@PLCC32 [DX3032]
CY7C287 [DX0001]
CY7C287@PLCC32 [DX3032]
CY7C289 [DX0001]
CY7C289@PLCC32 [DX3032]
CY7C291 [DX0001]
CY7C291@PLCC28 [DX3028]
CY7C291A [DX0001]
CY7C291A@PLCC28 [DX2028]
CY7C292 [DX0001]
CY7C292@PLCC28 [DX3028]
CY7C292A [DX0001]
CY7C292A@PLCC28 [DX2028]
CY7C293A [DX0001]
CY7C293A@PLCC28 [DX2028]
CY8C1354C-166AXC [DX3062]
SY14B101KA-ZS45X@SOIC44 [DX1010]
SY14B101LA-ZS20X@SOIC44 [DX1010]
SY14B104K-ZS25XI@SOIC44 [DX1010]

DRAM & SRAM

CY62128@SOIC32 [DX1020]
CY62128@SOJ32 [DX1039]
CY62128@VSOP32 [DX1003]
CY62128L@SOIC32 [DX1020]
CY62128L@SOJ32 [DX1039]
CY62128L@VSOP32 [DX1003]
CY62128LL@SOIC32 [DX1020]
CY62128LL@SOJ32
CY62128LL@VSOP32 [DX1003]
CY7C1061@TSOP54 [DX1010]
CY7C1061@VFBGA48 [UN]
CY7C192 [DX0001]
CY7C192@SOJ28 [DX1038]

PLD

CY22381@SOIC8 [DX1045]
CY22392@TSSOP16 [DX1000]
CY22393@TSSOP16 [DX1000]
CY22394@TSSOP16 [DX1000]
CY22395@TSSOP16 [DX1000]
CY2291@SOIC20 [DX1033]
CY2292@SOIC16 [DX1016]
CY2295@SSOP28 [DX1026]
CY37032@PLCC44 [DX2044]
CY37032@TQFP44 [DX3003]
CY37032V@PLCC44 [DX2044]
CY37032V@TQFP44 [DX3003]
CY37064@PLCC44 [DX2044]
CY37064@PLCC84 [DX2084]
CY37064@TQFP100 [DX3021]
CY37064@TQFP44 [DX3003]
CY37064V@PLCC44 [DX2044]
CY37064V@PLCC84 [DX2084]
CY37064V@TQFP100 [DX3021]
CY37064V@TQFP44 [DX3003]
CY37128@PLCC84 [DX2084]
CY37128@TQFP100 [DX3021]
CY37128@TQFP160 [DX3037]
CY37128V@PLCC84 [DX2084]
CY37128V@TQFP100 [DX3021]
CY37128V@TQFP160 [DX3037]
CY37192@TQFP160 [DX3037]
CY37192V@TQFP160 [DX3037]
CY37256@PQFP208 [DX3076]
CY37256@TQFP160 [DX3037]
CY37256V@PQFP208 [DX3076]
CY37256V@TQFP160 [DX3037]
CY37384@PQFP208 [DX3076]
CY37384V@PQFP208 [DX3076]

CY37512@PQFP208 [DX3076]
CY37512V@PQFP208 [DX3076]
CY7C342B@PGA68 [DX5000]
CY7C342B@PLCC68 [DX2068]
CY7C344B [DX0001]
CY7C344B@PLCC28 [DX2028]
CY7C346B@PLCC84 [DX2084]
CY7C346B@PQFP100 [DX3022]
CY7C371@PLCC44 [DX2044]
CY7C371@TQFP44 [DX3003]
CY7C371I@PLCC44 [DX2044]
CY7C371I@TQFP44 [DX3003]
CY7C372@PLCC44 [DX2044]
CY7C372@TQFP44 [DX3003]
CY7C372I@PLCC44 [DX2044]
CY7C372I@TQFP44 [DX3003]
CY7C373@PLCC84 [DX2084]
CY7C373@TQFP100 [DX3021]
CY7C373I@PLCC84 [DX2084]
CY7C373I@TQFP100 [DX3021]
CY7C374@PLCC84 [DX2084]
CY7C374@TQFP100 [DX3021]
CY7C374I@PLCC84 [DX2084]
CY7C374I@TQFP100 [DX3021]
PALC16L8 [DX0001]
PALC16L8@PLCC20 [DX2020]
PALC16L8L [DX0001]
PALC16L8L@PLCC20 [DX2020]
PALC16R4 [DX0001]
PALC16R4@PLCC20 [DX2020]
PALC16R4L [DX0001]
PALC16R4L@PLCC20 [DX2020]
PALC16R6 [DX0001]
PALC16R6@PLCC20 [DX2020]
PALC16R6L [DX0001]
PALC16R6L@PLCC20 [DX2020]
PALC16R8 [DX0001]
PALC16R8@PLCC20 [DX2020]
PALC16R8L [DX0001]
PALC16R8L@PLCC20 [DX2020]
PALC22V10 [DX0001]
PALC22V10@PLCC28 [DX2028]
PALC22V10A [DX0001]
PALC22V10A@PLCC28 [DX2028]
PALC22V10B [DX0001]
PALC22V10B@PLCC28 [DX2028]
PALC22V10D [DX0001]
PALC22V10D@PLCC28 [DX2028]
PALC22V10L [DX0001]
PALC22V10L@PLCC28 [DX2028]
PALCE16V8 [DX0001]
PALCE16V8@PLCC20 [DX2020]
PALCE20V8 [DX0001]
PALCE20V8@PLCC28 [DX2028]
PALCE20V8L [DX0001]
PALCE20V8L@PLCC28 [DX2028]
PALCE22V10 [DX0001]
PALCE22V10@PLCC28 [DX2028]
PLDC20G10 [DX0001]
PLDC20G10@PLCC28 [DX2028]
PLDC20G10B [DX0001]
PLDC20G10B@PLCC28 [DX2028]
PLDC20RA10 [DX0001]
PLDC20RA10@PLCC28 [DX0001]

MICROCONTROLLER

CG6457AM@SSOP20 [DX1026]
CG6457AM@SSOP20(ISP) [DX0001]
CG6457AMB@SSOP20 [DX1026]
CG6462AM@SOIC8 [DX1045]
CG6462AM@SOIC8(ISP) [DX0001]
CG6462AMB@SOIC8 [DX1045]
CY14B256@SOIC32 [DX1069]
CY14B256@SSOP48 [DX1028]
CY14B256L@SOIC32 [DX1069]
CY14B256L@SSOP48 [DX1028]
CY7C53120E2@SOIC32 [DX1020]
CY7C53120E2@TQFP44 [DX3002]
CY7C53120E2A@SOIC32 [DX1020]
CY7C53120E2A@TQFP44 [DX3002]
CY7C53120E4@SOIC32 [DX1020]
CY7C53120E4@TQFP44 [DX3002]
CY7C53120E4A@SOIC32 [DX1020]
CY7C53120E4A@TQFP44 [DX3002]
CY7C53150 [DX3013]
CY7C60113@SSOP28 [DX1026]
CY7C60113@SSOP28(ISP) [DX0001]
CY7C60113C@SSOP28 [DX1026]
CY7C60113C@SSOP28(ISP) [DX0001]
CY7C60123 [DX0001]

CY7C60123(ISP) [DX0001]
CY7C60123@SSOP48(ISP) [DX0001]
CY7C60123C(ISP) [DX0001]
CY7C60123C@SSOP48(ISP) [DX0001]
CY7C60223(ISP) [DX0001]
CY7C60223@QSOP24(ISP) [DX0001]
CY7C60223@SOIC24(ISP) [DX0001]
CY7C60223C(ISP) [DX0001]
CY7C60223C@QSOP24(ISP) [DX0001]
CY7C60223C@SOIC24(ISP) [DX0001]
CY7C60323@MLF32(ISP) [DX0001]
CY7C60323@SSOP28(ISP) [DX0001]
CY7C60323B@SSOP28 [DX1077]
CY7C60333@MLF32(ISP) [DX0001]
CY7C60413@QFN16 [DX4008]
CY7C60443@QFN32(ISP) [DX0001]
CY7C60445@QFN32(ISP) [DX0001]
CY7C60455@QFN48(ISP) [DX0001]
CY7C60456@QFN48(ISP) [DX0001]
CY7C63000@SOIC20 [DX1033]
CY7C63000A@SOIC20 [DX1033]
CY7C63000C@SOIC20 [DX1033]
CY7C63001@SOIC20 [DX1033]
CY7C63001A@SOIC20 [DX1033]
CY7C63001C@SOIC20 [DX1033]
CY7C63100@SOIC24 [DX1033]
CY7C63100A@SOIC24 [DX1033]
CY7C63100C@SOIC24 [DX1033]
CY7C63101@SOIC24 [DX1033]
CY7C63101A@SOIC24 [DX1033]
CY7C63101C@SOIC24 [DX1033]
CY7C63200@SOIC18 [DX1033]
CY7C63200A@SOIC18 [DX1033]
CY7C63200C@SOIC18 [DX1033]
CY7C63201@SOIC18 [DX1033]
CY7C63201A@SOIC18 [DX1033]
CY7C63201C@SOIC18 [DX1033]
CY7C63221A [DX0001]
CY7C63231@SOIC18 [DX1033]
CY7C63231A@SOIC18 [DX1033]
CY7C63310(ISP) [DX0001]
CY7C63310@SOIC16(ISP) [DX0001]
CY7C63310C(ISP) [DX0001]
CY7C63310C@SOIC16(ISP) [DX0001]
CY7C63411(dip48) [DX0001]
CY7C63411C(dip40) [DX0001]
CY7C63411C@SSOP48 [DX1028]
CY7C63412(dip48) [DX0001]
CY7C60123@SSOP48 [DX1028]
CY7C60123C [DX0001]
CY7C60123C@SSOP48 [DX1028]
CY7C60223 [DX0001]
CY7C60223@QSOP24 [DX1001]
CY7C60223@SOIC24 [DX1033]
CY7C60223C [DX0001]
CY7C60223C@QSOP24 [DX1001]
CY7C60223C@SOIC24 [DX1033]
CY7C60323@MLF32 [DX4015]
CY7C60323@SSOP28 [DX1077]
CY7C60323B@MLF32 [DX4015]
CY7C60333@MLF32 [DX4015]
CY7C60333B@MLF32 [DX4015]
CY7C60443@QFN32 [DX4015]
CY7C60445@QFN32 [DX4015]
CY7C60455@QFN48 [DX4021]
CY7C60456@QFN48 [DX4021]
CY7C63000 [DX0001]
CY7C63000A [DX0001]
CY7C63000C [DX0001]
CY7C63001 [DX0001]
CY7C63001A [DX0001]
CY7C63001C [DX0001]
CY7C63100 [DX0001]
CY7C63100A [DX0001]
CY7C63100C [DX0001]
CY7C63101 [DX0001]
CY7C63101A [DX0001]
CY7C63101C [DX0001]
CY7C63200 [DX0001]
CY7C63200A [DX0001]
CY7C63200C [DX0001]
CY7C63201 [DX0001]
CY7C63201A [DX0001]
CY7C63201C [DX0001]
CY7C63221 [DX0001]
CY7C63231 [DX0001]
CY7C63231A [DX0001]
CY7C63310 [DX0001]
CY7C63310@SOIC16 [DX1016]
CY7C63310C [DX0001]
CY7C63310C@SOIC16 [DX1016]
CY7C63411(dip40) [DX0001]
CY7C63411@SSOP48 [DX1028]
CY7C63411C(dip48) [DX0001]
CY7C63412(dip40) [DX0001]
CY7C63412@SSOP48 [DX1028]

CY7C63412C(dip40) [DX0001]
CY7C63412C@SSOP48 [DX1028]
CY7C63413(dip48) [DX0001]
CY7C63413C(dip40) [DX0001]
CY7C63413C@SSOP48 [DX1028]
CY7C63511@SSOP48 [DX1028]
CY7C63511C@SSOP48 [DX1028]
CY7C63512@SSOP48 [DX1028]
CY7C63512C@SSOP48 [DX1028]
CY7C63513@SSOP48 [DX1028]
CY7C63513C@SSOP48 [DX1028]
CY7C63722@SOIC18 [DX1033]
CY7C63722C@SOIC18 [DX1033]
CY7C63723@SOIC18 [DX1033]
CY7C63723C@SOIC18 [DX1033]
CY7C63742@QSOP24 [DX1025]
CY7C63742C [DX0001]
CY7C63742C@SOIC24 [DX1033]
CY7C63743@QSOP24 [DX1025]
CY7C63743C [DX0001]
CY7C63743C@SOIC24 [DX1033]
CY7C63801(ISP) [DX0001]
CY7C63801@SOIC16(ISP) [DX0001]
CY7C63801C(ISP) [DX0001]
CY7C63801C@SOIC16(ISP) [DX0001]
CY7C63803@SOIC16(ISP) [DX0001]
CY7C63803C@SOIC16(ISP) [DX0001]
CY7C63813(ISP) [DX0001]
CY7C63813@SOIC18(ISP) [DX0001]
CY7C63813C(ISP) [DX0001]
CY7C63813C@SOIC18(ISP) [DX0001]
CY7C63823(ISP) [DX0001]
CY7C63823@QSOP24(ISP) [DX0001]
CY7C63823@SOIC24(ISP) [DX0001]
CY7C63823C(ISP) [DX0001]
CY7C63823C@QSOP24(ISP) [DX0001]
CY7C63823C@SOIC24(ISP) [DX0001]
CY7C63833@QFN32(ISP) [DX0001]
CY7C63833C@QFN32(ISP) [DX0001]
CY7C63903@SSOP28(ISP) [DX0001]
CY7C63903C@SSOP28(ISP) [DX0001]
CY7C63913(ISP) [DX0001]
CY7C63913C(ISP) [DX0001]
CY7C63923@SSOP48(ISP) [DX0001]
CY7C63923C@SSOP48(ISP) [DX0001]
CY7C64011@SOIC28 [DX1033]
CY7C64011C@SOIC28 [DX1033]
CY7C64012@SOIC28 [DX1033]
CY7C63412C(dip48) [DX0001]
CY7C63413(dip40) [DX0001]
CY7C63413@SSOP48 [DX1028]
CY7C63413C(dip48) [DX0001]
CY7C63511(dip48) [DX0001]
CY7C63511C(dip48) [DX0001]
CY7C63512(dip48) [DX0001]
CY7C63512C(dip48) [DX0001]
CY7C63513(dip48) [DX0001]
CY7C63513C(dip48) [DX0001]
CY7C63722 [DX0001]
CY7C63722C [DX0001]
CY7C63723 [DX0001]
CY7C63723C [DX0001]
CY7C63742 [DX0001]
CY7C63742@SOIC24 [DX1033]
CY7C63742C@QSOP24 [DX1025]
CY7C63743 [DX0001]
CY7C63743@SOIC24 [DX1033]
CY7C63743C@QSOP24 [DX1025]
CY7C63801 [DX0001]
CY7C63801@SOIC16 [DX1016]
CY7C63801C [DX0001]
CY7C63801C@SOIC16 [DX1016]
CY7C63803@SOIC16 [DX1016]
CY7C63803C@SOIC16 [DX1016]
CY7C63813 [DX0001]
CY7C63813@SOIC18 [DX1033]
CY7C63813C [DX0001]
CY7C63813C@SOIC18 [DX1033]
CY7C63823 [DX0001]
CY7C63823@QSOP24 [DX1001]
CY7C63823@SOIC24 [DX1033]
CY7C63823C [DX0001]
CY7C63823C@QSOP24 [DX1001]
CY7C63823C@SOIC24 [DX1033]
CY7C63833@QFN32 [DX4015]
CY7C63833C@QFN32 [DX4015]
CY7C63903@SSOP28 [DX1026]
CY7C63903C@SSOP28 [DX1026]
CY7C63913 [DX0001]
CY7C63913C [DX0001]
CY7C63923@SSOP48 [DX1028]
CY7C63923C@SSOP48 [DX1028]
CY7C64011 [DX0001]
CY7C64011C [DX0001]
CY7C64012 [DX0001]
CY7C64012C [DX0001]

CY7C64012C@SOIC28 [DX1033]
CY7C64013@SOIC28 [DX1033]
CY7C64013C@SOIC28 [DX1033]
CY7C64111@SSOP48 [DX1028]
CY7C64111C@SSOP48 [DX1028]
CY7C64112@SSOP48 [DX1028]
CY7C64112C@SSOP48 [DX1028]
CY7C64113@SSOP48 [DX1028]
CY7C64113C@SSOP48 [DX1028]
CY7C64215@MLF56(ISP) [DX0001]
CY7C64215@SSOP28(ISP) [DX0001]
CY7C64315@QFN16(ISP) [DX0001]
CY7C64316@QFN16(ISP) [DX0001]
CY7C64343@QFN32(ISP) [DX0001]
CY7C64345@QFN32(ISP) [DX0001]
CY7C64355@QFN48(ISP) [DX0001]
CY7C64356@QFN48(ISP) [DX0001]
CY7C65013@SSOP48 [DX1028]
CY7C65013C@SSOP48 [DX1028]
CY7C65113@SOIC28 [DX1033]
CY7C65113C@SOIC28 [DX1033]
CY7C66011@SSOP48 [DX1028]
CY7C66011C@SSOP48 [DX1028]
CY7C66012@SSOP48 [DX1028]
CY7C66012C@SSOP48 [DX1028]
CY7C66013@SSOP48 [DX1028]
CY7C66013C@SSOP48 [DX1028]
CY7C66111@SSOP56 [DX1054]
CY7C66111C@QFN56 [DX4022]
CY7C66111C@TSOP56 [DX1055]
CY7C66112@SSOP56 [DX1054]
CY7C66112C@QFN56 [DX4022]
CY7C66112C@TSOP56 [DX1055]
CY7C66113@SSOP56 [DX1054]
CY7C66113C@QFN56 [DX4022]
CY7C66113C@TSOP56 [DX1055]
CY8C20000@MLF48(ISP) [DX0001]
CY8C20045-24SXI [DX1030]
CY8C20055-24SXI [DX1030]
CY8C20065-24SXI [DX1030]
CY8C20066A-24LTXI [DX4021]
CY8C20224@MLF16 [DX4008]
CY8C20234@MLF16 [DX4008]
CY8C20234@SOIC16 [DX1016]
CY8C20236A-24LKXI [DX4008]
CY8C20237@MLF16 [DX4008]
CY8C20237S@MLF16 [DX4008]
CY8C20246@QFN16 [DX4008]
CY7C64013 [DX0001]
CY7C64013C [DX0001]
CY7C64111 [DX0001]
CY7C64111C [DX0001]
CY7C64112 [DX0001]
CY7C64112C [DX0001]
CY7C64113 [DX0001]
CY7C64113C [DX0001]
CY7C64215@MLF56 [DX4022]
CY7C64215@SSOP28 [DX1026]
CY7C64315@QFN16 [DX4008]
CY7C64316@QFN16 [DX4008]
CY7C64343@QFN32 [DX4015]
CY7C64345@QFN32 [DX4015]
CY7C64355@QFN48 [DX4021]
CY7C64356@QFN48 [DX4021]
CY7C65013 [DX0001]
CY7C65013C [DX0001]
CY7C65113 [DX0001]
CY7C65113C [DX0001]
CY7C66011 [DX0001]
CY7C66011C [DX0001]
CY7C66012 [DX0001]
CY7C66012C [DX0001]
CY7C66013 [DX0001]
CY7C66013C [DX0001]
CY7C66111@QFN56 [DX4022]
CY7C66111@TSOP56 [DX1055]
CY7C66111C@SSOP56 [DX1054]
CY7C66112@QFN56 [DX4022]
CY7C66112@TSOP56 [DX1055]
CY7C66112C@SSOP56 [DX1054]
CY7C66113@QFN56 [DX4022]
CY7C66113@TSOP56 [DX1055]
CY7C66113C@SSOP56 [DX1054]
CY8C20000@MLF48 [DX4021]
CY8C20045-24LKXI [DX4008]
CY8C20055-24LKXI [DX4008]
CY8C20065-24LKXI [DX4008]
CY8C20066A@MLF48 [DX4021]
CY8C20134@SOIC8 [DX1045]
CY8C20224@MLF16(ISP) [DX0001]
CY8C20234@MLF16(ISP) [DX0001]
CY8C20236A@MLF16 [DX4008]
CY8C20236A-24LKXIT [DX4008]
CY8C20237@SOIC16 [DX1030]
CY8C20237S@SOIC16 [DX1030]
CY8C20246@QFN16(ISP) [DX0001]

CY8C20246A@MLF16 [DX4008]
CY8C20246A-24LKXI [DX4008]
CY8C20246A-24LKXIT [DX4008]
CY8C20246AS-24LKXI [DX4008]
CY8C20246AS-24LKXIT [DX4008]
CY8C20247@MLF16 [DX4008]
CY8C20247@SOIC16 [DX1030]
CY8C20247S@MLF16 [DX4008]
CY8C20247S@SOIC16 [DX1030]
CY8C20266@QFN16 [DX4008]
CY8C20266@QFN16(ISP) [DX0001]
CY8C20324@MLF24 [DX4012]
CY8C20324@MLF24(ISP) [DX0001]
CY8C20334@MLF24 [DX4012]
CY8C20334@MLF24(ISP) [DX0001]
CY8C20336A@MLF24 [DX4012]
CY8C20336A-24LQXI [DX4012]
CY8C20336A-24LQXIT [DX4012]
CY8C20336AN-24LQXI [DX4012]
CY8C20336AN-24LQXIT [DX4012]
CY8C20337@MLF24 [DX4012]
CY8C20337S@MLF24 [DX4012]
CY8C20346@QFN24 [DX4012]
CY8C20346@QFN24(ISP) [DX0001]
CY8C20346A@MLF24 [DX4012]
CY8C20346A-24LQXI [DX4012]
CY8C20346A-24LQXIT [DX4012]
CY8C20346AS-24LQXI [DX4012]
CY8C20346AS-24LQXIT [DX4012]
CY8C20347@MLF24 [DX4012]
CY8C20347S@MLF24 [DX4012]
CY8C20366@QFN24 [DX4012]
CY8C20366@QFN24(ISP) [DX0001]
CY8C20396A@MLF24 [DX4012]
CY8C20396A-24LQXI [DX4012]
CY8C20396A-24LQXIT [DX4012]
CY8C20397@MLF24 [DX4012]
CY8C20397S@MLF24 [DX4012]
CY8C20424@MLF32 [DX4015]
CY8C20424@MLF32(ISP) [DX0001]
CY8C20434@MLF32 [DX4015]
CY8C20434@MLF32(ISP) [DX0001]
CY8C20436A@MLF32 [DX4015]
CY8C20436A-24LQXI [DX4015]
CY8C20436A-24LQXIT [DX4015]
CY8C20436AN-24LQXI [DX4015]
CY8C20436AN-24LQXIT [DX4015]
CY8C20437@MLF32 [DX4015]
CY8C20437S@MLF32 [DX4015]
CY8C20446@QFN32 [DX4015]
CY8C20446@QFN32(ISP) [DX0001]
CY8C20446A@MLF32 [DX4015]
CY8C20446A-24LQXI [DX4015]
CY8C20446A-24LQXIT [DX4015]
CY8C20446AS-24LQXI [DX4015]
CY8C20446AS-24LQXIT [DX4015]
CY8C20447@MLF32 [DX4015]
CY8C20447S@MLF32 [DX4015]
CY8C20466@QFN32 [DX4015]
CY8C20466@QFN32(ISP) [DX0001]
CY8C20466A@MLF32 [DX4015]
CY8C20466A-24LQXI [DX4015]
CY8C20466A-24LQXIT [DX4015]
CY8C20466AS-24LQXI [DX4015]
CY8C20466AS-24LQXIT [DX4015]
CY8C20467@MLF32 [DX4015]
CY8C20467S@MLF32 [DX4015]
CY8C20496A@MLF32 [DX4015]
CY8C20496A-24LQXI [DX4015]
CY8C20496A-24LQXIT [DX4015]
CY8C20497@MLF32 [DX4015]
CY8C20497S@MLF32 [DX4015]
CY8C20524@SSOP28 [DX1077]
CY8C20534@BGA30 [DX0001]
CY8C20534@SSOP28 [DX1077]
CY8C20534@SSOP28(ISP) [DX0001]
CY8C20536A@SSOP48 [DX1028]
CY8C20536A-24PVXI [DX1028]
CY8C20536A-24PVXIT [DX1028]
CY8C20537@SSOP48 [DX1028]
CY8C20537S@SSOP48 [DX1028]
CY8C20546@SSOP48 [DX1028]
CY8C20546@SSOP48(ISP) [DX0001]
CY8C20546A@SSOP48 [DX1028]
CY8C20546A-24PVXI [DX1028]
CY8C20546A-24PVXIT [DX1028]
CY8C20547@SSOP48 [DX1028]
CY8C20547S@SSOP48 [DX1028]
CY8C20566@SSOP48 [DX1028]
CY8C20566@SSOP48(ISP) [DX0001]
CY8C20566A@SSOP48 [DX1028]
CY8C20566A-24PVXI [DX1028]
CY8C20566A-24PVXIT [DX1028]
CY8C20567@SSOP48 [DX1028]
CY8C20567S@SSOP48 [DX1028]
CY8C20636A@MLF48 [DX4021]

CY8C20636A-24LQXI [DX4043]
CY8C20636A-24LQXIT [DX4043]
CY8C20636A-24LTXI [DX4021]
CY8C20636A-24LTXIT [DX4021]
CY8C20636AN-24LTXI [DX4021]
CY8C20636AN-24LTXIT [DX4021]
CY8C20637@MLF48 [DX4043]
CY8C20637S@MLF48 [DX4043]
CY8C20646@QFN48 [DX4021]
CY8C20646@QFN48(ISP) [DX0001]
CY8C20646A@MLF48 [DX4021]
CY8C20646A-24LQXI [DX4043]
CY8C20646A-24LQXIT [DX4043]
CY8C20646A-24LTXI [DX4021]
CY8C20646A-24LTXIT [DX4021]
CY8C20647@MLF48 [DX4043]
CY8C20647S@MLF48 [DX4043]
CY8C20666@QFN48 [DX4021]
CY8C20666@QFN48(ISP) [DX0001]
CY8C20666A@MLF48 [DX4021]
CY8C20666A-24LQXI [DX4043]
CY8C20666A-24LQXIT [DX4043]
CY8C20666A-24LTXI [DX4021]
CY8C20666A-24LTXIT [DX4021]
CY8C20666AS-24LTXI [DX4021]
CY8C20666AS-24LTXIT [DX4021]
CY8C20667@MLF48 [DX4043]
CY8C20667S@MLF48 [DX4043]
CY8C20746A-24FDXC [BBBB]
CY8C20746A-24FDXCT [BBBB]
CY8C20747-24FDXC [BBBB]
CY8C20766A-24FDXC [DX4043]
CY8C20766A-24FDXCT [DX4043]
CY8C20767-24FDXC [BBBB]
CY8C21123@SOIC8 [DX1045]
CY8C21123@SOIC8(ISP) [DX0001]
CY8C21123B@SOIC8 [DX1045]
CY8C21223@SOIC16 [DX1016]
CY8C21223@SOIC16(ISP) [DX0001]
CY8C21223B@SOIC16 [DX1016]
CY8C21234@SOIC16 [DX1016]
CY8C21234@SOIC16(ISP) [DX0001]
CY8C21234B@SOIC16 [DX1016]
CY8C21312-12PVXE [DX1026]
CY8C21323@MLF24 [DX4012]
CY8C21323@MLF24(ISP) [DX0001]
CY8C21323@SSOP20 [DX1026]
CY8C21323@SSOP20(ISP) [DX0001]
CY8C21323B@MLF24 [DX4012]
CY8C21323B@SSOP20 [DX1026]
CY8C21334@SSOP20 [DX1026]
CY8C21334@SSOP20(ISP) [DX0001]
CY8C21334B@SSOP20 [DX1026]
CY8C21345@SOIC28 [DX1033]
CY8C21345@SSOP28 [DX1026]
CY8C21434@MLF32 [DX4015]
CY8C21434@MLF32(ISP) [DX0001]
CY8C21434B@MLF32 [DX4015]
CY8C21512-12PVXE [DX1033]
CY8C21534@SSOP28 [DX1077]
CY8C21534@SSOP28(ISP) [DX0001]
CY8C21534B@SSOP28 [DX1077]
CY8C21634@MLF32 [DX4015]
CY8C21634@MLF32(ISP) [DX0001]
CY8C21634B@MLF32 [DX4015]
CY8C22345@SOIC28 [DX1033]
CY8C22345@SSOP28 [DX1026]
CY8C22545@TQFP44 [DX3005]
CY8C24123 [DX0001]
CY8C24123(ISP) [DX0001]
CY8C24123@SOIC8 [DX1016]
CY8C24123@SOIC8(ISP) [DX0001]
CY8C24123A [DX0001]
CY8C24123A(ISP) [DX0001]
CY8C24123A@SOIC8 [DX1016]
CY8C24123A@SOIC8(ISP) [DX0001]
CY8C24193@QFN32 [DX4015]
CY8C24223 [DX0001]
CY8C24223(ISP) [DX0001]
CY8C24223@SOIC20 [DX1033]
CY8C24223@SOIC20(ISP) [DX0001]
CY8C24223@SSOP20 [DX1026]
CY8C24223@SSOP20(ISP) [DX0001]
CY8C24223A [DX0001]
CY8C24223A(ISP) [DX0001]
CY8C24223A@SOIC20 [DX1033]
CY8C24223A@SOIC20(ISP) [DX0001]
CY8C24223A@SSOP20 [DX1026]
CY8C24223A@SSOP20(ISP) [DX0001]
CY8C24423 [DX0001]
CY8C24423(ISP) [DX0001]
CY8C24423@MLF32 [DX4015]
CY8C24423@MLF32(ISP) [DX0001]
CY8C24423@SOIC28 [DX1033]
CY8C24423@SOIC28(ISP) [DX0001]
CY8C24423@SSOP28 [DX1026]

CY8C24423@SSOP28(ISP) [DX0001]
CY8C24423A(ISP) [DX0001]
CY8C24423A@MLF32(ISP) [DX0001]
CY8C24423A@SOIC28(ISP) [DX0001]
CY8C24423A@SSOP28(ISP) [DX0001]
CY8C24533(ISP) [DX0001]
CY8C24533@SOIC28(ISP) [DX0001]
CY8C24533@SSOP28(ISP) [DX0001]
CY8C24533A(ISP) [DX0001]
CY8C24533A@SOIC28(ISP) [DX0001]
CY8C24533A@SSOP28(ISP) [DX0001]
CY8C24533C@SOIC28 [DX1033]
CY8C24633 [DX0001]
CY8C24633@SOIC28 [DX1033]
CY8C24633@SSOP28 [DX1077]
CY8C24633A [DX0001]
CY8C24633A@SOIC28 [DX1033]
CY8C24633A@SSOP28 [DX1077]
CY8C24633C [DX0001]
CY8C24633C@SSOP28 [DX1077]
CY8C24794@MLF56(ISP) [DX0001]
CY8C24894@MLF56(ISP) [DX0001]
CY8C24994@MLF68(ISP) [DX0001]
CY8C25122(ISP) [DX0001]
CY8C25122C(ISP) [DX0001]
CY8C26233(ISP) [DX0001]
CY8C26233@SOIC20(ISP) [DX0001]
CY8C26233@SSOP20(ISP) [DX0001]
CY8C26233C(ISP) [DX0001]
CY8C26233C@SOIC20(ISP) [DX0001]
CY8C26233C@SSOP20(ISP) [DX0001]
CY8C26443(ISP) [DX0001]
CY8C26443@SOIC28(ISP) [DX0001]
CY8C26443@SSOP28(ISP) [DX0001]
CY8C26443C(ISP) [DX0001]
CY8C26443C@SOIC28(ISP) [DX0001]
CY8C26443C@SSOP28(ISP) [DX0001]
CY8C26643(ISP) [DX0001]
CY8C26643@SSOP48(ISP) [DX0001]
CY8C26643@TQFP44(ISP) [DX0001]
CY8C26643C(ISP) [DX0001]
CY8C26643C@SSOP48(ISP) [DX0001]
CY8C26643C@TQFP44(ISP) [DX0001]
CY8C27143(ISP) [DX0001]
CY8C27243(ISP) [DX0001]
CY8C27243@SOIC20(ISP) [DX0001]
CY8C27243@SSOP20(ISP) [DX0001]
CY8C27443(ISP) [DX0001]
CY8C24423A [DX0001]
CY8C24423A@MLF32 [DX4015]
CY8C24423A@SOIC28 [DX1033]
CY8C24423A@SSOP28 [DX1026]
CY8C24533 [DX0001]
CY8C24533@SOIC28 [DX1033]
CY8C24533@SSOP28 [DX1077]
CY8C24533A [DX0001]
CY8C24533A@SOIC28 [DX1033]
CY8C24533A@SSOP28 [DX1077]
CY8C24533C [DX0001]
CY8C24533C@SSOP28 [DX1077]
CY8C24633(ISP) [DX0001]
CY8C24633@SOIC28(ISP) [DX0001]
CY8C24633@SSOP28(ISP) [DX0001]
CY8C24633A(ISP) [DX0001]
CY8C24633A@SOIC28(ISP) [DX0001]
CY8C24633A@SSOP28(ISP) [DX0001]
CY8C24633C@SOIC28 [DX1033]
CY8C24794@MLF56 [DX4022]
CY8C24894@MLF56 [DX4022]
CY8C24994@MLF68 [DX4028]
CY8C25122 [DX0001]
CY8C25122C [DX0001]
CY8C26233 [DX0001]
CY8C26233@SOIC20 [DX1033]
CY8C26233@SSOP20 [DX1026]
CY8C26233C [DX0001]
CY8C26233C@SOIC20 [DX1033]
CY8C26233C@SSOP20 [DX1026]
CY8C26443 [DX0001]
CY8C26443@SOIC28 [DX1033]
CY8C26443@SSOP28 [DX1026]
CY8C26443C [DX0001]
CY8C26443C@SOIC28 [DX1033]
CY8C26443C@SSOP28 [DX1026]
CY8C26643 [DX0001]
CY8C26643@SSOP48 [DX1028]
CY8C26643@TQFP44 [DX3003]
CY8C26643C [DX0001]
CY8C26643C@SSOP48 [DX1028]
CY8C26643C@TQFP44 [DX3003]
CY8C27143 [DX0001]
CY8C27243 [DX0001]
CY8C27243@SOIC20 [DX1033]
CY8C27243@SSOP20 [DX1026]
CY8C27443 [DX0001]
CY8C27443@SOIC28 [DX1033]

CY8C27443@SOIC28(ISP) [DX0001]
CY8C27443@SSOP28(ISP) [DX0001]
CY8C27466(ISP) [DX0001]
CY8C27466@SSOP28(ISP) [DX0001]
CY8C27543@TQFP44(ISP) [DX0001]
CY8C27566@TQFP44(ISP) [DX0001]
CY8C27643@MLF48(ISP) [DX0001]
CY8C27643@SSOP48(ISP) [DX0001]
CY8C27666@MLF48(ISP) [DX0001]
CY8C27666@SSOP48(ISP) [DX0001]
CY8C27866@TQFP100(ISP) [DX0001]
CY8C28403@SSOP28 [DX1026]
CY8C28433@SSOP28 [DX1026]
CY8C28452@SSOP28 [DX1026]
CY8C28533@TQFP44 [DX3005]
CY8C28623@QFN48 [DX4021]
CY8C28645@QFN48 [DX4021]
CY8C29466(ISP) [DX0001]
CY8C29466@SSOP28(ISP) [DX0001]
CY8C29566@TQFP44(ISP) [DX0001]
CY8C29666@MLF48(ISP) [DX0001]
CY8C29666@SSOP48(ISP) [DX0001]
CY8C29866@TQFP100(ISP) [DX0001]
CY8C3244LTI-123 [DX4021]
CY8C3244PVI-133 [DX1028]
CY8C3245AXI-166 [DX3021]
CY8C3245LTI-139 [DX4021]
CY8C3245LTI-163 [DX4026]
CY8C3245PVI-150 [DX1028]
CY8C3246AXI-138 [DX3021]
CY8C3246LTI-128 [DX4026]
CY8C3246LTI-162 [DX4021]
CY8C3246PVI-147 [DX1028]
CY8C3444LTI-110 [DX4026]
CY8C3444PVI-100 [DX1028]
CY8C3445AXI-108 [DX3021]
CY8C3445LTI-078 [DX4021]
CY8C3445LTI-081 [DX4026]
CY8C3445PVI-090 [DX1028]
CY8C3446AXI-099 [DX3021]
CY8C3446LTI-073 [DX4021]
CY8C3446LTI-083 [DX4021]
CY8C3446PVI-091 [DX1028]
CY8C3665AXI-010 [DX3021]
CY8C3665LTI-006 [DX4021]
CY8C3665PVI-007 [DX1028]
CY8C3665PVI-080 [DX1028]
CY8C3666AXI-037 [DX3021]
CY8C27443@SSOP28 [DX1026]
CY8C27466 [DX0001]
CY8C27466@SSOP28 [DX1026]
CY8C27543@TQFP44 [DX3005]
CY8C27566@TQFP44 [DX3005]
CY8C27643@MLF48 [DX4021]
CY8C27643@SSOP48 [DX1028]
CY8C27666@MLF48 [DX4021]
CY8C27666@SSOP48 [DX1028]
CY8C27866@TQFP100 [DX3005]
CY8C28243@SSOP20 [DX1026]
CY8C28413@SSOP28 [DX1026]
CY8C28445@SSOP28 [DX1026]
CY8C28513@TQFP44 [DX3005]
CY8C28545@TQFP44 [DX3005]
CY8C28643@QFN48 [DX4021]
CY8C29466 [DX0001]
CY8C29466@SSOP28 [DX1026]
CY8C29566@TQFP44 [DX3005]
CY8C29666@MLF48 [DX4021]
CY8C29666@SSOP48 [DX1028]
CY8C29866@TQFP100 [DX3043]
CY8C3244AXI-153 [DX3021]
CY8C3244LTI-130 [DX4026]
CY8C3245AXI-158 [DX3021]
CY8C3245LTI-129 [DX4026]
CY8C3245LTI-144 [DX4021]
CY8C3245PVI-134 [DX1028]
CY8C3246AXI-131 [DX3021]
CY8C3246LTI-125 [DX4021]
CY8C3246LTI-149 [DX4026]
CY8C3246PVI-122 [DX1028]
CY8C3444AXI-116 [DX3021]
CY8C3444LTI-119 [DX4021]
CY8C3445AXI-104 [DX3021]
CY8C3445LTI [DX4026]
CY8C3445LTI-079 [DX4026]
CY8C3445LTI-089 [DX4021]
CY8C3445PVI-094 [DX1028]
CY8C3446AXI-105 [DX3021]
CY8C3446LTI-074 [DX4026]
CY8C3446LTI-085 [DX4026]
CY8C3446PVI-102 [DX1028]
CY8C3665AXI-016 [DX3021]
CY8C3665LTI-044 [DX4026]
CY8C3665PVI-008 [DX1028]
CY8C3666AXI-036 [DX3021]
CY8C3666AXI-052 [DX3021]

CY8C3666LTI-027 [DX4026]
CY8C3865AXI-019 [DX3021]
CY8C3865LTI-062 [DX4021]
CY8C3865PVI-063 [DX1028]
CY8C3866AXI-039 [DX3021]
CY8C3866LTI-030 [DX4026]
CY8C3866LTI-068 [DX4021]
CY8C3866PVI-070 [DX1028]
CY8C4245AXI-483@TQFP44 [DX3003]
CY8CLED01D01@QFN56 [DX4022]
CY8CLED01DOCD1@QFN56 [DX4022]
CY8CLED02D01@QFN56 [DX4022]
CY8CLED02DOCD1@QFN56 [DX4022]
CY8CLED03D01@QFN56 [DX4022]
CY8CLED03DOCD1@QFN56 [DX4022]
CY8CLED04@QFN68 [DX4026]
CY8CLED04D01@QFN56 [DX4022]
CY8CLED04DOCD1@QFN56 [DX4022]
CY8CLED08@QFN48 [DX4021]
CY8CLED08@SSOP28 [DX1026]
CY8CLED08@SSOP48 [DX1028]
CY8CLED16@QFN48 [DX4021]
CY8CLED16@SSOP28 [DX1026]
CY8CLED16@SSOP48 [DX1028]
CY8CNP102B@LQFP100 [DX3021]
CY8CTMA1036BUI [DX5234]
CY8CTMA120@QFN56 [DX4022]
CY8CTMA140@QFN48 [DX4043]
CY8CTMA140E@QFN48 [DX4043]
CY8CTMA300@QFN48 [DX4043]
CY8CTMA300E@QFN48 [DX4043]
CY8CTMA301@QFN36 [DX4042]
CY8CTMA301E@QFN36 [DX4042]
CY8CTMA340@QFN36 [DX4042]
CY8CTMA340E@QFN36 [DX4042]
CY8CTMA341@QFN36 [DX4042]
CY8CTMA341E@QFN36 [DX4042]
CY8CTMA375@QFN36 [DX4042]
CY8CTMA375E@QFN36 [DX4042]
CY8CTMA400-44LQI [BBBB]
CY8CTMA400-49FNI [BBBB]
CY8CTMA400-60BUI [DX5252]
CY8CTMA461-48LQI [DX4043]
CY8CTMA461-56LQI [DX4087]
CY8CTMA463-44LQI [BBBB]
CY8CTMA463-49FNI [BBBB]
CY8CTMA463-60BUI [DX5252]
CY8CTMA466-48LQI [DX4043]
CY8C3666LTI-050 [DX4021]
CY8C3865LTI-014 [DX4026]
CY8C3865PVI-060 [DX1028]
CY8C3866AXI-035 [DX3021]
CY8C3866AXI-040 [DX3021]
CY8C3866LTI-067 [DX4021]
CY8C3866PVI-021 [DX1028]
CY8C4125AXI-483@TQFP44 [DX3003]
CY8C4245AZI-483@TQFP48 [DX3007]
CY8CLED01D02@QFN56 [DX4022]
CY8CLED01DOCD2@QFN56 [DX4022]
CY8CLED02D02@QFN56 [DX4022]
CY8CLED02DOCD2@QFN56 [DX4022]
CY8CLED03D02@QFN56 [DX4022]
CY8CLED03DOCD2@QFN56 [DX4022]
CY8CLED04@QFN68(ISP) [DX0001]
CY8CLED04D02@QFN56 [DX4022]
CY8CLED04DOCD2@QFN56 [DX4022]
CY8CLED08@QFN48(ISP) [DX0001]
CY8CLED08@SSOP28(ISP) [DX0001]
CY8CLED08@SSOP48(ISP) [DX0001]
CY8CLED16@QFN48(ISP) [DX0001]
CY8CLED16@SSOP28(ISP) [DX0001]
CY8CLED16@SSOP48(ISP) [DX0001]
CY8CNP102E@LQFP100 [DX3021]
CY8CTMA110@QFN32 [DX4015]
CY8CTMA140@QFN36 [DX4042]
CY8CTMA140E@QFN36 [DX4042]
CY8CTMA300@QFN36 [DX4042]
CY8CTMA300E@QFN36 [DX4042]
CY8CTMA300E-BCSP [DX0001]
CY8CTMA301@QFN48 [DX4043]
CY8CTMA301E@QFN48 [DX4043]
CY8CTMA340@QFN48 [DX4043]
CY8CTMA340E@QFN48 [DX4043]
CY8CTMA341@QFN48 [DX4043]
CY8CTMA341E@QFN48 [DX4043]
CY8CTMA375@QFN48 [DX4043]
CY8CTMA375E@QFN48 [DX4043]
CY8CTMA400-48LQI [DX4043]
CY8CTMA400-56LQI [DX4087]
CY8CTMA461-44LQI [BBBB]
CY8CTMA461-49FNI [BBBB]
CY8CTMA461-60BUI [DX5252]
CY8CTMA463-48LQI [DX4043]
CY8CTMA463-56LQI [DX4087]
CY8CTMA466-44LQI [BBBB]
CY8CTMA466-49FNI [BBBB]

CY8CTMA466-56LQI [DX4087]
CY8CTMA466-60BUI [DX5252]
CY8CTMA467-44LQI [BBBB]
CY8CTMA467-48LQI [DX4043]
CY8CTMA467-49FNI [BBBB]
CY8CTMA467-56LQI [DX4087]
CY8CTMA467-60BUI [DX5252]
CY8CTMA468-44LQI [BBBB]
CY8CTMA468-48LQI [DX4043]
CY8CTMA468-49FNI [BBBB]
CY8CTMA468-56LQI [DX4087]
CY8CTMA468-60BUI [DX5252]
CY8CTMA473-44LQI [BBBB]
CY8CTMA473-48LQI [DX4043]
CY8CTMA473-49FNI [BBBB]
CY8CTMA473-56LQI [DX4087]
CY8CTMA473-60BUI [DX5252]
CY8CTMA768BUI [DX5234]
CY8CTMD200@QFN16 [DX4008]
CY8CTMD200@QFN24 [DX4012]
CY8CTMD200@QFN32 [DX4015]
CY8CTMD200@QFN48 [DX4021]
CY8CTMD200@SSOP48 [DX1028]
CY8CTMD200A@QFN16 [DX4008]
CY8CTMD200A@QFN24 [DX4012]
CY8CTMD200A@QFN32 [DX4015]
CY8CTMD200A@QFN48 [DX4021]
CY8CTMD200A@SSOP48 [DX1028]
CY8CTMD201@QFN16 [DX4008]
CY8CTMD201@QFN24 [DX4012]
CY8CTMD201@QFN32 [DX4015]
CY8CTMD201@QFN48 [DX4021]
CY8CTMD201@SSOP48 [DX1028]
CY8CTMD201A@QFN16 [DX4008]
CY8CTMD201A@QFN24 [DX4012]
CY8CTMD201A@QFN32 [DX4015]
CY8CTMD201A@QFN48 [DX4021]
CY8CTMD201A@SSOP48 [DX1028]
CY8CTMG110@QFN32 [DX4015]
CY8CTMG120@QFN56 [DX4022]
CY8CTMG200 [DX0001]
CY8CTMG200@QFN16 [DX4008]
CY8CTMG200@QFN24 [DX4012]
CY8CTMG200@QFN32 [DX4015]
CY8CTMG200@QFN48 [DX4021]
CY8CTMG200@SSOP48 [DX1028]
CY8CTMG200A [DX0001]
CY8CTMG200A@QFN16 [DX4008]
CY8CTMG200A@QFN24 [DX4012]
CY8CTMG200A@QFN32 [DX4015]
CY8CTMG200A@QFN48 [DX4021]
CY8CTMG200A@SSOP48 [DX1028]
CY8CTMG201 [DX0001]
CY8CTMG201@QFN16 [DX4008]
CY8CTMG201@QFN24 [DX4012]
CY8CTMG201@QFN32 [DX4015]
CY8CTMG201@QFN48 [DX4021]
CY8CTMG201@SSOP48 [DX1028]
CY8CTMG201A [DX0001]
CY8CTMG201A@QFN16 [DX4008]
CY8CTMG201A@QFN24 [DX4012]
CY8CTMG201A@QFN32 [DX4015]
CY8CTMG201A@QFN48 [DX4021]
CY8CTMG201A@SSOP48 [DX1028]
CY8CTMG240 [DX0001]
CY8CTMG240@QFN16 [DX4008]
CY8CTMG240@QFN24 [DX4012]
CY8CTMG240@QFN32 [DX4015]
CY8CTMG240@QFN48 [DX4021]
CY8CTMG240@SSOP48 [DX1028]
CY8CTMG240A [DX0001]
CY8CTMG240A@QFN16 [DX4008]
CY8CTMG240A@QFN24 [DX4012]
CY8CTMG240A@QFN32 [DX4015]
CY8CTMG240A@QFN48 [DX4021]
CY8CTMG240A@SSOP48 [DX1028]
CY8CTMG300@QFN36 [DX4042]
CY8CTMG300@QFN48 [DX4043]
CY8CTMG300E@QFN36 [DX4042]
CY8CTMG300E@QFN48 [DX4043]
CY8CTMG301@QFN36 [DX4042]
CY8CTMG301@QFN48 [DX4043]
CY8CTMG301E@QFN36 [DX4042]
CY8CTMG301E@QFN48 [DX4043]
CY8CTMG340@QFN36 [DX4042]
CY8CTMG340@QFN48 [DX4043]
CY8CTMG340E@QFN36 [DX4042]
CY8CTMG340E@QFN48 [DX4043]
CY8CTMG341@QFN36 [DX4042]
CY8CTMG341@QFN48 [DX4043]
CY8CTMG341E@QFN36 [DX4042]
CY8CTMG341E@QFN48 [DX4043]
CY8CTST110@QFN32 [DX4015]
CY8CTST120@QFN56 [DX4022]
CY8CTST200@QFN16 [DX4008]
CY8CTST200@QFN24 [DX4012]

CY8CTST200@QFN32 [DX4015]
CY8CTST200@QFN48 [DX4021]
CY8CTST200@SSOP48 [DX1028]
CY8CTST200A@QFN16 [DX4008]
CY8CTST200A@QFN24 [DX4012]
CY8CTST200A@QFN32 [DX4015]
CY8CTST200A@QFN48 [DX4021]
CY8CTST200A@SSOP48 [DX1028]
CY8CTST201@QFN16 [DX4008]
CY8CTST201@QFN24 [DX4012]
CY8CTST201@QFN32 [DX4015]
CY8CTST201@QFN48 [DX4021]
CY8CTST201@SSOP48 [DX1028]
CY8CTST201A@QFN16 [DX4008]
CY8CTST201A@QFN24 [DX4012]
CY8CTST201A@QFN32 [DX4015]
CY8CTST201A@QFN48 [DX4021]
CY8CTST201A@SSOP48 [DX1028]
CY8CTST240@QFN16 [DX4008]
CY8CTST240@QFN24 [DX4012]
CY8CTST240@QFN32 [DX4015]
CY8CTST240@QFN48 [DX4021]
CY8CTST240@SSOP48 [DX1028]
CY8CTST240A@QFN16 [DX4008]
CY8CTST240A@QFN24 [DX4012]
CY8CTST240A@QFN32 [DX4015]
CY8CTST240A@QFN48 [DX4021]
CY8CTST240A@SSOP48 [DX1028]
CY8CTST241 [DX0001]
CY8CTST241@QFN16 [DX4008]
CY8CTST241@QFN24 [DX4012]
CY8CTST241@QFN32 [DX4015]
CY8CTST241@QFN48 [DX4021]
CY8CTST241@SSOP48 [DX1028]
CY8CTST241A [DX0001]
CY8CTST241A@QFN16 [DX4008]
CY8CTST241A@QFN24 [DX4012]
CY8CTST241A@QFN32 [DX4015]
CY8CTST241A@QFN48 [DX4021]
CY8CTST241A@SSOP48 [DX1028]
CY8CTST242 [DX0001]
CY8CTST242@QFN16 [DX4008]
CY8CTST242@QFN24 [DX4012]
CY8CTST242@QFN32 [DX4015]
CY8CTST242@QFN48 [DX4021]
CY8CTST242@SSOP48 [DX1028]
CY8CTST242A [DX0001]
CY8CTST242A@QFN16 [DX4008]
CY8CTST242A@QFN24 [DX4012]
CY8CTST242A@QFN32 [DX4015]
CY8CTST242A@QFN48 [DX4021]
CY8CTST242A@SSOP48 [DX1028]
CY8CTST300@QFN36 [DX4042]
CY8CTST300@QFN48 [DX4043]
CY8CTST300E@QFN36 [DX4042]
CY8CTST300E@QFN48 [DX4043]
CY8CTST301@QFN36 [DX4042]
CY8CTST301@QFN48 [DX4043]
CY8CTST301E@QFN36 [DX4042]
CY8CTST301E@QFN48 [DX4043]
CY8CTST340@QFN36 [DX4042]
CY8CTST340@QFN48 [DX4043]
CY8CTST340E@QFN36 [DX4042]
CY8CTST340E@QFN48 [DX4043]
CY8CTST341@QFN36 [DX4042]
CY8CTST341@QFN48 [DX4043]
CY8CTST341E@QFN36 [DX4042]
CY8CTST341E@QFN48 [DX4043]
CYBL10161-56LQXI [DX4089]
CYBL10162-56LQXI [DX4089]
CYBL10163-56LQXI [DX4089]
CYBL10461-56LQXI [DX4089]
CYBL10462-56LQXI [DX4089]
CYBL10463-56LQXI [DX4089]
CYBL10561-56LQXI [DX4089]
CYBL10562-56LQXI [DX4089]
CYBL10563-56LQXI [DX4089]
CYBL10563-68FNXI [BBBB]
CYPD1103-35FNXI [BBBB]
CYPD1120-40LQXI [DX4017]
CYPD1121-40LQXI [DX4017]
CYPD1122-40LQXI [DX4017]
CYPD1131-28PVXI [DX1026]
CYPD1131-35FNXI [BBBB]
CYPD1134-28PVXI [DX1026]
CYPD1134-40LQXI [DX4017]
CYPD1201-28PVXI [DX1026]
CYRF69103@QFN40 [DX4017]
CYRF69103@QFN40(ISP) [DX0001]
CYRF69103C@QFN40 [DX4017]
CYRF69103C@QFN40(ISP) [DX0001]
CYRF69213@QFN40 [DX4017]
CYRF69213@QFN40(ISP) [DX0001]
CYRF69213C@QFN40 [DX4017]
CYRF69213C@QFN40(ISP) [DX0001]

CYROD

MICROCONTROLLER

CRD89C4051 [DX0001]
CRD89C51 [DX0001]
CRD89C51@TQFP44 [DX3002]
CRD89C512RD@PLCC44 [DX2044]
CRD89C51AA [DX0001]
CRD89C51AA@TQFP44 [DX3002]
CRD89C51AA1TB@PLCC44 [DX2044]
CRD89C51AA1TB@TQFP48 [DX3007]
CRD89C51AB1T@PLCC44 [DX2044]
CRD89C51AB1T@TQFP48 [DX3007]
CRD89C51AB1TA@PLCC44 [DX2044]
CRD89C51AB1TA@TQFP48 [DX3007]
CRD89C51AB1TB@PLCC44 [DX2044]
CRD89C51AB1TB@TQFP48 [DX3007]
CRD89C51AC1T@PLCC44 [DX2044]
CRD89C51AC1T@TQFP48 [DX3007]
CRD89C51AD@PLCC44 [DX2044]
CRD89C51AD1T [DX0001]
CRD89C51AD1T@TQFP44 [DX3002]
CRD89C51AR1TB [DX0001]
CRD89C51AR1TB@TQFP44 [DX3002]
CRD89C51RA [DX0001]
CRD89C51RA@TQFP44 [DX3002]
CRD89C51RA2(ISP) [DX0001]
CRD89C51RA2@PLCC44(ISP) [DX0001]
CRD89C51RA2@TQFP44(ISP) [DX0001]
CRD89C51RB@PLCC44 [DX2044]
CRD89C51RB2 [DX0001]
CRD89C51RB2@PLCC44 [DX2044]
CRD89C51RB2@TQFP44 [DX3002]
CRD89C51RC [DX0001]
CRD89C51RC@TQFP44 [DX3002]
CRD89C51RD [DX0001]
CRD89C51RD@TQFP44 [DX3002]
CRD89C51RE [DX0001]
CRD89C51RE@TQFP44 [DX3002]
CRD89C665@PLCC44 [DX2044]
CRD89L4051 [DX0001]
CRD89L51 [DX0001]
CRD89L51@TQFP44 [DX3002]
CRD89L51AA1TB@PLCC44 [DX2044]
CRD89L51AA1TB@TQFP48 [DX3007]
CRD89C4051@SOIC20 [DX1031]
CRD89C51@PLCC44 [DX2044]
CRD89C512RD [DX0001]
CRD89C512RD@TQFP44 [DX3002]
CRD89C51AA@PLCC44 [DX2044]
CRD89C51AA1TB [DX0001]
CRD89C51AA1TB@TQFP44 [DX3002]
CRD89C51AB1T [DX0001]
CRD89C51AB1T@TQFP44 [DX3002]
CRD89C51AB1TA [DX0001]
CRD89C51AB1TA@TQFP44 [DX3002]
CRD89C51AB1TB [DX0001]
CRD89C51AB1TB@TQFP44 [DX3002]
CRD89C51AC1T [DX0001]
CRD89C51AC1T@TQFP44 [DX3002]
CRD89C51AD [DX0001]
CRD89C51AD@TQFP44 [DX3002]
CRD89C51AD1T@PLCC44 [DX2044]
CRD89C51AD1T@TQFP48 [DX3007]
CRD89C51AR1TB@PLCC44 [DX2044]
CRD89C51AR1TB@TQFP48 [DX3007]
CRD89C51RA@PLCC44 [DX2044]
CRD89C51RA2 [DX0001]
CRD89C51RA2@PLCC44 [DX2044]
CRD89C51RA2@TQFP44 [DX3002]
CRD89C51RB [DX0001]
CRD89C51RB@TQFP44 [DX3002]
CRD89C51RB2(ISP) [DX0001]
CRD89C51RB2@PLCC44(ISP) [DX0001]
CRD89C51RB2@TQFP44(ISP) [DX0001]
CRD89C51RC@PLCC44 [DX2044]
CRD89C51RC1T@TQFP64 [DX3011]
CRD89C51RD@PLCC44 [DX2044]
CRD89C51RD1T@TQFP64 [DX3011]
CRD89C51RE@PLCC44 [DX2044]
CRD89C665 [DX0001]
CRD89C665@TQFP44 [DX3002]
CRD89L4051@SOIC20 [DX1031]
CRD89L51@PLCC44 [DX2044]
CRD89L51AA1TB [DX0001]
CRD89L51AA1TB@TQFP44 [DX3002]
CRD89L51AB1T [DX0001]

CRD89L51AB1T@PLCC44 [DX2044]
CRD89L51AB1T@TQFP44 [DX3002]
CRD89L51AB1T@TQFP48 [DX3007]
CRD89L51AB1TA [DX0001]
CRD89L51AB1TA@PLCC44 [DX2044]
CRD89L51AB1TA@TQFP44 [DX3002]
CRD89L51AB1TA@TQFP48 [DX3007]
CRD89L51AB1TB [DX0001]
CRD89L51AB1TB@PLCC44 [DX2044]
CRD89L51AB1TB@TQFP44 [DX3002]
CRD89L51AB1TB@TQFP48 [DX3007]
CRD89L51AC1T [DX0001]
CRD89L51AC1T@PLCC44 [DX2044]
CRD89L51AC1T@TQFP44 [DX3002]
CRD89L51AC1T@TQFP48 [DX3007]
CRD89L51AD [DX0001]
CRD89L51AD@PLCC44 [DX2044]
CRD89L51AD@TQFP44 [DX3002]
CRD89L51AD1T [DX0001]
CRD89L51AD1T@PLCC44 [DX2044]
CRD89L51AD1T@TQFP44 [DX3002]
CRD89L51AD1T@TQFP48 [DX3007]
CRD89L51AR1TB [DX0001]
CRD89L51AR1TB@PLCC44 [DX2044]
CRD89L51AR1TB@TQFP44 [DX3002]
CRD89L51AR1TB@TQFP48 [DX3007]
CRD89L51RA [DX0001]
CRD89L51RA@PLCC44 [DX2044]
CRD89L51RA@TQFP44 [DX3002]
CRD89L51RA2 [DX0001]
CRD89L51RA2(ISP) [DX0001]
CRD89L51RA2@PLCC44 [DX2044]
CRD89L51RA2@PLCC44(ISP) [DX0001]
CRD89L51RA2@TQFP44 [DX3002]
CRD89L51RA2@TQFP44(ISP) [DX0001]
CRD89L51RB [DX0001]
CRD89L51RB@PLCC44 [DX2044]
CRD89L51RB@TQFP44 [DX3002]
CRD89L51RB2 [DX0001]
CRD89L51RB2(ISP) [DX0001]
CRD89L51RB2@PLCC44 [DX2044]
CRD89L51RB2@PLCC44(ISP) [DX0001]
CRD89L51RB2@TQFP44 [DX3002]
CRD89L51RB2@TQFP44(ISP) [DX0001]
CRD89L51RC [DX0001]
CRD89L51RC@PLCC44 [DX2044]
CRD89L51RC@TQFP44 [DX3002]
CRD89L51RC1T@TQFP64 [DX3011]
CRD89L51RD [DX0001]
CRD89L51RD@PLCC44 [DX2044]
CRD89L51RD@TQFP44 [DX3002]
CRD89L51RD1T@TQFP64 [DX3011]
CRD89L665 [DX0001]
CRD89L665@PLCC44 [DX2044]
CRD89L665@TQFP44 [DX3002]

DALLAS

E(E)PROM/FRAM/NVRAM

DS1073M-100 [DX0001]
DS1073M-60 [DX0001]
DS1073M-66 [DX0001]
DS1073M-80 [DX0001]
DS1073Z-100@SOIC8 [DX1045]
DS1073Z-60@SOIC8 [DX1045]
DS1073Z-66@SOIC8 [DX1045]
DS1073Z-80@SOIC8 [DX1045]
DS1077LU-100 [DX0001]
DS1077LU-120 [DX0001]
DS1077LU-125 [DX0001]
DS1077LU-133 [DX0001]
DS1077LU-40 [DX0001]
DS1077LU-50 [DX0001]
DS1077LU-60 [DX0001]
DS1077LU-66 [DX0001]
DS1077LZ-100 [DX1045]
DS1077LZ-120 [DX1045]
DS1077LZ-125 [DX1045]
DS1077LZ-133 [DX1045]
DS1077LZ-40@SOIC8 [DX1045]
DS1077LZ-50@SOIC8 [DX1045]
DS1077LZ-60@SOIC8 [DX1045]
DS1077LZ-66@SOIC8 [DX1045]
DS1077U-100 [DX0001]
DS1077U-120 [DX0001]
DS1077U-125 [DX0001]
DS1077U-133 [DX0001]

DS1077U-40 [DX0001]
DS1077U-50 [DX0001]
DS1077U-60 [DX0001]
DS1077U-66 [DX0001]
DS1077Z-100 [DX1045]
DS1077Z-120 [DX1045]
DS1077Z-125 [DX1045]
DS1077Z-133 [DX1045]
DS1077Z-40@SOIC8 [DX1045]
DS1077Z-50@SOIC8 [DX1045]
DS1077Z-60@SOIC8 [DX1045]
DS1077Z-66@SOIC8 [DX1045]
DS1086U [DX0001]
DS1086Z [DX1045]
DS1220AB [DX0001]
DS1220AD [DX0001]
DS1220Y [DX0001]
DS1225AB [DX0001]
DS1225AD [DX0001]
DS1225D [DX0001]
DS1225E [DX0001]
DS1225Y [DX0001]
DS1230AB [DX0001]
DS1230ABP [DX2068]
DS1230W [DX0001]
DS1230Y [DX0001]
DS1230YP [DX2068]
DS1235AB [DX0001]
DS1235Y [DX0001]
DS1243Y [DX0001]
DS1244 [DX0001]
DS1244P [DX2068]
DS1244Y [DX0001]
DS1244YP [DX2068]
DS1245AB [DX0001]
DS1245EE [DX0001]
DS1245P [DX2068]
DS1245W [DX0001]
DS1245Y [DX0001]
DS1248P [DX2068]
DS1248W [DX0001]
DS1248Y [DX0001]
DS1249AB [DX0001]
DS1249W [DX0001]
DS1249Y [DX0001]
DS1250AB [DX0001]
DS1250ABP [DX2068]
DS1250W [DX0001]
DS1250Y [DX0001]
DS1250YP [DX2068]
DS1251AB [DX0001]
DS1251P [DX2068]
DS1251W [DX0001]
DS1251Y [DX0001]
DS1256P [DX2068]
DS1256W [DX0001]
DS1256Y [DX0001]
DS1258AB [DX0001]
DS1258W [DX0001]
DS1258Y [DX0001]
DS1265AB [DX0001]
DS1265W [DX0001]
DS1265Y [DX0001]
DS1270AB [DX0001]
DS1270W [DX0001]
DS1270Y [DX0001]
DS1284 [DX0001]
DS1284N [DX0001]
DS1284Q@PLCC28 [DX2028]
DS1284QN@PLCC28 [DX2028]
DS1286 [DX0001]
DS1286I [DX0001]
DS1287 [DX0001]
DS1287A [DX0001]
DS12887 [DX0001]
DS12887A [DX0001]
DS12C887 [DX0001]
DS12C887+ [DX0001]
DS12C887A [DX0001]
DS1330AB [DX0001]
DS1330ABP [DX2068]
DS1330WP [DX2068]
DS1330Y [DX0001]
DS1330YP [DX2068]
DS1345AB [DX0001]
DS1345P [DX2068]
DS1345W [DX0001]
DS1345Y [DX0001]
DS1350AB [DX0001]
DS1350P [DX2068]
DS1350W [DX0001]
DS1350Y [DX0001]
DS1385 [DX0001]
DS1386(32K) [DX0001]
DS1386(8K) [DX0001]
DS1387 [DX0001]

DS14285 [DX0001]
DS14287 [DX0001]
DS1485 [DX0001]
DS1485@SOIC28 [DX1035]
DS1486 [DX0001]
DS1486P [DX2068]
DS1488 [DX0001]
DS1501 [DX0001]
DS1511 [DX0001]
DS1553 [DX0001]
DS1553P [DX2068]
DS1553W [DX0001]
DS1553WP [DX2068]
DS1554 [DX0001]
DS1554W [DX0001]
DS1556 [DX0001]
DS1630AB [DX0001]
DS1630ABL [DX2068]
DS1630Y [DX0001]
DS1630YL [DX2068]
DS1642 [DX0001]
DS1643 [DX0001]
DS1643P [DX2068]
DS1644 [DX0001]
DS1644P [DX2068]
DS1644PS [DX2068]
DS1645AB [DX0001]
DS1645ABP [DX2068]
DS1645EE [DX0001]
DS1645Y [DX0001]
DS1645YP [DX2068]
DS1646 [DX0001]
DS1646P [DX2068]
DS1647 [DX0001]
DS1647LPM [DX2068]
DS1650AB [DX0001]
DS1650ABP [DX2068]
DS1650Y [DX2068]
DS1650YP [DX0001]
DS1685-3 [DX0001]
DS1685-3@SOP24 [DX1033]
DS1685-5 [DX0001]
DS1685-5@SOP24 [DX1033]
DS1687-3 [DX0001]
DS1687-5 [DX0001]
DS17287-3 [DX0001]
DS17287-5 [DX0001]
DS1742 [DX0001]
DS1742W [DX0001]
DS1743 [DX0001]
DS1743P [DX2068]
DS1743W [DX0001]
DS1743WP [DX2068]
DS1744 [DX0001]
DS1744P [DX2068]
DS1744W [DX0001]
DS1744WP [DX2068]
DS1746 [DX0001]
DS1746P [DX2068]
DS1747 [DX0001]
DS1747P [DX2068]
DS1747PS [DX2068]
DS1747W [DX0001]
DS1747WP [DX2068]
DS1747WPS [DX2068]
DS17487-3 [DX0001]
DS17487-5 [DX0001]
DS17887-3 [DX0001]
DS17887-5 [DX0001]
DS2406@TO-92 [DX0001]
DS2406P@TSOC6 [DX1066]
DS2430A@TO-92 [DX0001]
DS2430AP@TSOC6 [DX1066]
DS2431@TDFN6 [DX4000]
DS2431@TO-92 [DX0001]
DS2431P@TSOC6 [DX1066]
DS2432P@TSOC6 [DX1066]
DS2433@PR-35 [DX0001]
DS2433S(3.9)@SOIC8 [DX1045]
DS2433S(5.5)@SOIC8 [DX1044]
DS2460@SOIC8 [DX1016]
DS2502 [DX0001]
DS2502P@TSOC6 [DX1066]
DS2502S@SOIC8 [DX1045]
DS2502UNW [DX0001]
DS2502UNW@SOIC8 [DX1045]
DS2502UNW@SOT-23 [DX1041]
DS2502UNW@TSOC6 [DX1066]
DS2505 [DX0001]
DS2505S@TSOC6 [DX1066]
DS2506 [DX0001]
DS2506S@SOIC8 [DX1044]
DS4510@uSOP10 [DX1016]
DS4520@TSSOP16 [DX1000]
DS4550@TSSOP20 [DX1000]

MICROCONTROLLER

DS5000[32K] [DX0001]
DS5000T[32K] [DX0001]
DS87C520 [DX0001]
DS87C520@TQFP44 [DX3003]
DS87C550@PLCC68 [DX2068]
DS89C420(rev.A) [DX0001]
DS89C420(rev.A)@TQFP44 [DX3003]
DS89C420@TQFP44 [DX3003]
DS89C430@PLCC44 [DX2044]
DS89C440 [DX0001]
DS89C440@TQFP44 [DX3003]
DS89C450@PLCC44 [DX2044]
DS5000[8K] [DX0001]
DS5000T[8K] [DX0001]
DS87C520@PLCC44 [DX2044]
DS87C530@PLCC52 [DX2052]
DS89C420 [DX0001]
DS89C420(rev.A)@PLCC44 [DX2044]
DS89C420@PLCC44 [DX2044]
DS89C430 [DX0001]
DS89C430@TQFP44 [DX3003]
DS89C440@PLCC44 [DX2044]
DS89C450 [DX0001]
DS89C450@TQFP44 [DX3003]

DENSE-PAC

E(E)PROM/FRAM/NVRAM

DPV27C101 [DX0001]
DPV27C256 [DX0001]
DPV27C512 [DX0001]
DPV27C101@PLCC32 [DX2032]
DPV27C256@PLCC32 [DX2032]
DPV27C512@PLCC32 [DX2032]

DEUTRON

E(E)PROM/FRAM/NVRAM

AC25LV010 [DX0001]
AC25LV512 [DX0001]
P439LV010@PLCC32 [DX2032]
P439LV040@PLCC32 [DX2032]
P439LV088@TSOP48 [DX1004]
AC25LV010@SOIC8 [DX1045#1]
AC25LV512@SOIC8 [DX1045#1]
P439LV010@VSOP32 [DX1003]
P439LV040@VSOP32 [DX1003]
P439VF800@TSOP48 [DX1004]

DYCMCU

MICROCONTROLLER

G80F915@QFP44 [DX3005]
G80F923@QFP48 [DX3007]
G80F925@QFP64 [DX3085]
G80F935@QFP64 [DX3085]
G80F939@QFP100 [DX3021]
G80F915@QFP48 [DX3007]
G80F924@QFP64 [DX3085]
G80F927D@QFP64 [DX3011]
G80F937@QFP80 [DX3016]

EASTSOFT

MICROCONTROLLER

HR7P169FGD [DX0001]
HR7P169FGD@ISP [DX0001]
HR7P169FGDD [DX0001]
HR7P169FGDD@ISP [DX0001]
HR7P169FGNF [DX4011]
HR7P169FGS [DX1033]
HR7P169FGS@ISP [DX0001]
HR7P169FGS3 [DX1016]
HR7P169FGS3@ISP [DX0001]
HR7P169FGS4 [DX1016]
HR7P169FGS4@ISP [DX0001]
HR7P169FGS5 [DX1045]
HR7P169FGS5@ISP [DX0001]
HR7P169FGTF [DX1000]
HR7P169FGTF@ISP [DX0001]
HR7P170FHD [DX0001]
HR7P170FHD@ISP [DX0001]
HR7P170FHS [DX1033]
HR7P170FHS@ISP [DX0001]
HR7P170FHS3 [DX1016]
HR7P170FHS3@ISP [DX0001]
HR7P170FHS4 [DX1016]
HR7P170FHS4@ISP [DX0001]
HR7P170FHS5 [DX1045]
HR7P170FHS5@ISP [DX0001]
HR7P201FHD [DX0001]
HR7P201FHD@ISP [DX0001]
HR7P201FHS [DX1033]
HR7P201FHS@ISP [DX0001]
HR7P201FHS3 [DX1016]
HR7P201FHS3@ISP [DX0001]
HR7P201FHS4 [DX1016]
HR7P201FHS4@ISP [DX0001]
HR7P201FHS5 [DX1045]
HR7P201FHS5@ISP [DX0001]
SSC1650(EUI) [DX3007]
SSC1650@QFP48 [DX3007]

ECHELON

MICROCONTROLLER

CY7C53150 [DX3013]

E-CMOS

E(E)PROM/FRAM/NVRAM

EC24C01 [DX0001]
EC24C01@DFN8 [DX4047]
EC24C01@SOIC8 [DX1045]
EC24C01@TSSOP8 [DX1059]
EC24C02 [DX0001]
EC24C02@DFN8 [DX4047]
EC24C02@SOIC8 [DX1045]
EC24C02@TSSOP8 [DX1059]
EC24C02A [DX0001]
EC24C02A@DFN8 [DX4047]
EC24C02A@SOIC8 [DX1045]
EC24C02A@TSSOP8 [DX1059]
EC24C04 [DX0001]
EC24C04@DFN8 [DX4047]
EC24C04@SOIC8 [DX1045]
EC24C04@TSSOP8 [DX1059]
EC24C04A [DX0001]
EC24C04A@DFN8 [DX4047]
EC24C04A@SOIC8 [DX1045]
EC24C04A@TSSOP8 [DX1059]
EC24C08 [DX0001]
EC24C08@DFN8 [DX4047]
EC24C08@SOIC8 [DX1045]
EC24C08@TSSOP8 [DX1059]

EC24C08A [DX0001]
EC24C08A@DFN8 [DX4047]
EC24C08A@SOIC8 [DX1045]
EC24C08A@TSSOP8 [DX1059]
EC24C128 [DX0001]
EC24C128@DFN8 [DX4047]
EC24C128@SOIC8 [DX1045]
EC24C128@TSSOP8 [DX1059]
EC24C16 [DX0001]
EC24C16@DFN8 [DX4047]
EC24C16@SOIC8 [DX1045]
EC24C16@TSSOP8 [DX1059]
EC24C16A [DX0001]
EC24C16A@DFN8 [DX4047]
EC24C16A@SOIC8 [DX1045]
EC24C16A@TSSOP8 [DX1059]
EC24C256 [DX0001]
EC24C256@DFN8 [DX4047]
EC24C256@SOIC8 [DX1045]
EC24C256@TSSOP8 [DX1059]
EC24C32 [DX0001]
EC24C32@DFN8 [DX4047]
EC24C32@SOIC8 [DX1045]
EC24C32@TSSOP8 [DX1059]
EC24C64 [DX0001]
EC24C64@DFN8 [DX4047]
EC24C64@SOIC8 [DX1045]
EC24C64@TSSOP8 [DX1059]

EETI

MICROCONTROLLER

PCAP7800@QFN32 [DX4015]
PCAP7800@QFN48 [DX4043]

EFST

E(E)PROM/FRAM/NVRAM

EM25LV010@SOIC8 [DX1045]
EM25LV010@VFQFPN8 [DX4006]
EM25LV512@SOIC8 [DX1045]
EM25LV512@VFQFPN8 [DX4006]
F49B002UA [DX0001]
F49B002UA@PLCC32 [DX2032]
F49L004BA@PLCC32 [DX2032]
F49L004BA@TSOP40 [DX1006]
F49L004UA@PLCC32 [DX2032]
F49L004UA@TSOP40 [DX1006]
F49L040A@PLCC32 [DX2032]
F49L040A@VSOP32 [DX1003]
F49L160BA@TSOP48 [DX1004]
F49L160UA@TSOP48 [DX1004]
F49L400BA@TSOP48 [DX1004]
F49L400UA@TSOP48 [DX1004]
F49L800BA@TSOP48 [DX1004]
F49L800UA@TSOP48 [DX1004]

eGalax

MICROCONTROLLER

PCAP7800@QFN32 [DX4015]
PCAP7800@QFN48 [DX4043]

ELECTRONIC ARRAYS

E(E)PROM/FRAM/NVRAM

EA2716 [DX0001]

ELPIDA

E(E)PROM/FRAM/NVRAM

EHD0010A1MA@FBGA137 [DX5012]
EHD013011MA@FBGA137 [DX5012]
EHD013111MA@FBGA107 [DX5028]
EHD013221MA@FBGA107 [DX5028]
HF0030A17B@FBGA137 [DX5011]

EM

MICROCONTROLLER

EM6580@SOIC14 [DX1016]
EM6580@SOIC8 [DX1045]
EM68128@TSSOP24 [DX1000]
EM6819F2-A000@TSSOP28 [DX1001]
EM6819F2-B000@TSSOP28 [DX1001]
EM6819F2-B300@QFN20 [DX4011]
EM6819F2-B300@TSSOP16 [DX1067]
EM6819F2-B300@TSSOP20 [DX1067]
EM6819F2-B300@TSSOP28 [DX1001]
EM6819F4-A000@TSSOP28 [DX1001]
EM6819F4-B000@TSSOP28 [DX1001]
EM6819F4-B100@TSSOP28 [DX1001]
EM6819F4-B300@QFN20 [DX4011]
EM6819F4-B300@TSSOP16 [DX1067]
EM6819F4-B300@TSSOP20 [DX1067]
EM6819F4-B300@TSSOP28 [DX1001]
EM6819F6-A000@TSSOP28 [DX1001]
EM6819F6-A100@TSSOP28 [DX1001]
EM6819F6-B004@TSSOP28 [DX1001]
EM6819F6-B100@TSSOP28 [DX1001]
EM6819F6-B300@QFN20 [DX4011]
EM6819F6-B300@TSSOP16 [DX1067]
EM6819F6-B300@TSSOP20 [DX1067]
EM6819F6-B300@TSSOP28 [DX1001]

EMTC

E(E)PROM/FRAM/NVRAM

EM24C02 [DX0001]
EM24C02@SOIC8 [DX1045]
EM24C02@TSSOP8 [DX1059]
EM24C04 [DX0001]
EM24C04@SOIC8 [DX1045]
EM24C04@TSSOP8 [DX1059]
EM24C08 [DX0001]
EM24C08@SOIC8 [DX1045]
EM24C08@TSSOP8 [DX1059]
EM24C16 [DX0001]
EM24C16@SOIC8 [DX1045]
EM24C16@TSSOP8 [DX1059]
EM25SL512@SOIC8 [DX1045]
EM29SF002AB [DX0001]
EM29SF002AB@PLCC32 [DX2032]
EM29SF002AB@TSOP32 [DX1002]
EM29SF002AT [DX0001]
EM29SF002AT@PLCC32 [DX2032]
EM29SF002AT@TSOP32 [DX1002]
EM29SF002NAB [DX0001]
EM29SF002NAB@PLCC32 [DX2032]
EM29SF002NAB@TSOP32 [DX1002]
EM29SF002NAT [DX0001]
EM29SF002NAT@PLCC32 [DX2032]
EM29SF002NAT@TSOP32 [DX1002]

ENERGY

MICROCONTROLLER

EFM32LG230F128@QFN64 [DX4070-2]
EFM32LG230F256@QFN64 [DX4070-2]
EFM32LG230F64@QFN64 [DX4070-2]
EFM32LG232F128@TQFP64 [DX3011-10]
EFM32LG232F256@TQFP64 [DX3011-10]
EFM32LG232F64@TQFP64 [DX3011-10]
EFM32LG280F128@QFP100 [DX3043-6]
EFM32LG280F256@QFP100 [DX3043-6]
EFM32LG280F64@QFP100 [DX3043-6]
EFM32LG290F128@BGA112 [DX5058-1]
EFM32LG290F256@BGA112 [DX5058-1]
EFM32LG290F64@BGA112 [DX5058-1]
EFM32LG330F128@QFN64 [DX4070-2]
EFM32LG330F256@QFN64 [DX4070-2]
EFM32LG330F64@QFN64 [DX4070-2]
EFM32LG332F128@TQFP64 [DX3011-10]
EFM32LG332F256@TQFP64 [DX3011-10]
EFM32LG332F64@TQFP64 [DX3011-10]
EFM32LG380F128@QFP100 [DX3043-6]
EFM32LG380F256@QFP100 [DX3043-6]
EFM32LG380F64@QFP100 [DX3043-6]
EFM32LG390F128@BGA112 [DX5058-1]
EFM32LG390F256@BGA112 [DX5058-1]
EFM32LG390F64@BGA112 [DX5058-1]
EFM32LG840F128@QFN64 [DX4070-2]
EFM32LG840F256@QFN64 [DX4070-2]
EFM32LG840F64@QFN64 [DX4070-2]
EFM32LG842F128@TQFP64 [DX3011-10]
EFM32LG842F256@TQFP64 [DX3011-10]
EFM32LG842F64@TQFP64 [DX3011-10]
EFM32LG880F128@QFP100 [DX3043-6]
EFM32LG880F256@QFP100 [DX3043-6]
EFM32LG880F64@QFP100 [DX3043-6]
EFM32LG890F128@BGA112 [DX5058-1]
EFM32LG890F256@BGA112 [DX5058-1]
EFM32LG890F64@BGA112 [DX5058-1]
EFM32LG940F128@QFN64 [DX4070-2]
EFM32LG940F256@QFN64 [DX4070-2]
EFM32LG940F64@QFN64 [DX4070-2]
EFM32LG942F128@TQFP64 [DX3011-10]
EFM32LG942F256@TQFP64 [DX3011-10]
EFM32LG942F64@TQFP64 [DX3011-10]
EFM32LG980F128@QFP100 [DX3043-6]
EFM32LG980F256@QFP100 [DX3043-6]
EFM32LG980F64@QFP100 [DX3043-6]
EFM32LG990F128@BGA112 [DX5058-1]
EFM32LG990F256@BGA112 [DX5058-1]
EFM32LG990F64@BGA112 [DX5058-1]
EFM32TG108F16@QFN24 [DX4034-1]
EFM32TG108F32@QFN24 [DX4034-1]
EFM32TG108F4@QFN24 [DX4034-1]
EFM32TG108F8@QFN24 [DX4034-1]
EFM32TG110F16@QFN24 [DX4034-1]
EFM32TG110F32@QFN24 [DX4034-1]
EFM32TG110F4@QFN24 [DX4034-1]
EFM32TG110F8@QFN24 [DX4034-1]
EFM32TG210F16@QFN32 [DX4086-1]
EFM32TG210F32@QFN32 [DX4086-1]
EFM32TG210F8@QFN32 [DX4086-1]
EFM32TG222F16@TQFP48 [DX3007-6]
EFM32TG222F32@TQFP48 [DX3007-6]
EFM32TG222F8@TQFP48 [DX3007-6]
EFM32TG225F16@BGA48 [DX5237-1]
EFM32TG225F32@BGA48 [DX5237-1]
EFM32TG225F8@BGA48 [DX5237-1]
EFM32TG230F16@QFN64 [DX4070-2]
EFM32TG230F32@QFN64 [DX4070-2]
EFM32TG230F8@QFN64 [DX4070-2]
EFM32TG232F16@TQFP64 [DX3011-10]
EFM32TG232F32@TQFP64 [DX3011-10]
EFM32TG232F8@TQFP64 [DX3011-10]
EFM32TG822F16@TQFP48 [DX3007-6]
EFM32TG822F32@TQFP48 [DX3007-6]
EFM32TG822F8@TQFP48 [DX3007-6]
EFM32TG825F16@BGA48 [DX5237-1]
EFM32TG825F32@BGA48 [DX5237-1]
EFM32TG825F8@BGA48 [DX5237-1]
EFM32TG840F16@QFN64 [DX4070-2]
EFM32TG840F32@QFN64 [DX4070-2]

EFM32TG840F8@QFN64 [DX4070-2]
EFM32TG842F16@TQFP64 [DX3011-10]
EFM32TG842F32@TQFP64 [DX3011-10]
EFM32TG842F8@TQFP64 [DX3011-10]
EFM32ZG110F16@QFN24 [DX4034-1]
EFM32ZG110F32@QFN24 [DX4034-1]
EFM32ZG110F4@QFN24 [DX4034-1]

EON

E(E)PROM/FRAM/NVRAM

EN25B05(Bottom Boot)@SOP8(4.0) [DX1045]
EN25B05(Bottom Boot)@SOP8(5.4) [DX1044]
EN25B05(Bottom Boot)@VDFN8 [DX4005]
EN25B05(Top Boot)@SOP8(4.0) [DX1045]
EN25B05(Top Boot)@SOP8(5.4) [DX1044]
EN25B05(Top Boot)@VDFN8 [DX4005]
EN25B10(Bottom Boot)@SOP8(4.0) [DX1045]
EN25B10(Bottom Boot)@SOP8(5.4) [DX1044]
EN25B10(Bottom Boot)@VDFN8 [DX4005]
EN25B10(Top Boot)@SOP8(4.0) [DX1045]
EN25B10(Top Boot)@SOP8(5.4) [DX1044]
EN25B10(Top Boot)@VDFN8 [DX4005]
EN25B16(Bottom Boot)@SOP8 [DX1044#1]
EN25B16(Bottom Boot)@SOP8(ISP) [DX0001]
EN25B16(Bottom Boot)@VFQFN8(ISP) [DX0001]
EN25B16(Bottom Boot)@VFQFPN8 [DX4006#1]
EN25B16(Top Boot)@SOP8 [DX1044#1]
EN25B16(Top Boot)@SOP8(ISP) [DX0001]
EN25B16(Top Boot)@VFQFN8(ISP) [DX0001]
EN25B16(Top Boot)@VFQFPN8 [DX4006#1]
EN25B20(Bottom Boot)@SOP8(4.0) [DX1045#1]
EN25B20(Bottom Boot)@SOP8(5.4) [DX1044#1]
EN25B20(Bottom Boot)@VDFN8 [DX4005#1]
EN25B20(Top Boot)@SOP8(4.0) [DX1045#1]
EN25B20(Top Boot)@SOP8(5.4) [DX1044#1]
EN25B20(Top Boot)@VDFN8 [DX4005#1]
EN25B32(Bottom Boot)@SOP16 [DX1033#1]
EN25B32(Bottom Boot)@SOP16(ISP) [DX1033#1]
EN25B32(Bottom Boot)@SOP8 [DX1044#1]
EN25B32(Bottom Boot)@SOP8(ISP) [DX0001]
EN25B32(Bottom Boot)@VDFN8 [DX4006#1]
EN25B32(Bottom Boot)@VDFN8(ISP) [DX0001]
EN25B32(Top Boot)@SOP16 [DX1033#1]
EN25B32(Top Boot)@SOP16(ISP) [DX1033#1]
EN25B32(Top Boot)@SOP8 [DX1044#1]
EN25B32(Top Boot)@SOP8(ISP) [DX0001]
EN25B32(Top Boot)@VDFN8 [DX4006#1]
EN25B32(Top Boot)@VDFN8(ISP) [DX0001]

EN25B40(Bottom Boot)@SOP8(4.0) [DX1045#1]
EN25B40(Bottom Boot)@SOP8(5.4) [DX1044#1]
EN25B40(Bottom Boot)@VDFN8 [DX4005#1]
EN25B40(Top Boot)@SOP8(4.0) [DX1045#1]
EN25B40(Top Boot)@SOP8(5.4) [DX1044#1]
EN25B40(Top Boot)@VDFN8 [DX4005#1]
EN25B64(Bottom Boot)@SOP16 [DX1033#1]
EN25B64(Bottom Boot)@SOP16(ISP) [DX1033#1]
EN25B64(Bottom Boot)@VDFN8 [DX4006#1]
EN25B64(Bottom Boot)@VDFN8(ISP) [DX0001]
EN25B64(Top Boot)@SOP16 [DX1033#1]
EN25B64(Top Boot)@SOP16(ISP) [DX1033#1]
EN25B64(Top Boot)@VDFN8 [DX4006#1]
EN25B64(Top Boot)@VDFN8(ISP) [DX0001]
EN25B80(Bottom Boot)@SOP8(4.0) [DX1045#1]
EN25B80(Bottom Boot)@SOP8(5.4) [DX1044#1]
EN25B80(Bottom Boot)@VDFN8 [DX4005#1]
EN25B80(Top Boot)@SOP8(4.0) [DX1045#1]
EN25B80(Top Boot)@SOP8(5.4) [DX1044#1]
EN25B80(Top Boot)@VDFN8 [DX4005#1]
EN25D16 [DX0001]
EN25D16@SOP16 [DX1072#1]
EN25D16@SOP8 [DX1044#1]
EN25D16@VDFN8 [DX4006#1]
EN25D80 [DX0001]
EN25D80@SOP8 [DX1044#1]
EN25D80@VDFN8 [DX4005#1]
EN25F05@SOP8(4.0) [DX1045#1]
EN25F05@SOP8(5.4) [DX1044#1]
EN25F05@VDFN8 [DX4005#1]
EN25F10@SOP8(4.0) [DX1045#1]
EN25F10@SOP8(5.4) [DX1044#1]
EN25F10@VDFN8 [DX4005#1]
EN25F16 [DX0001]
EN25F16@SOP16 [DX1072#1]
EN25F16@SOP8 [DX1044#1]
EN25F16@VDFN8 [DX4006#1]
EN25F20@SOP8(4.0) [DX1045#1]
EN25F20@SOP8(5.4) [DX1044#1]
EN25F20@VDFN8 [DX4005#1]
EN25F32 [DX0001]
EN25F32@SOP16 [DX1033#1]
EN25F32@SOP8 [DX1044#1]
EN25F32@VDFN8 [DX4006#1]
EN25F40(fast mode)@SOP8(150mil) [DX1045#1]
EN25F40(fast mode)@SOP8(200mil) [DX1044#1]
EN25F40(fast mode)@VDFN8 [DX4005#1]
EN25F40@SOP8(150mil) [DX1045#1]
EN25F40@SOP8(200mil) [DX1044#1]
EN25F40@VDFN8 [DX4005#1]
EN25F64@DFN8 [DX4006#1]
EN25F64@SOP16 [DX1033#1]
EN25F64@SOP8 [DX1044#1]
EN25F64@VDFN8 [DX4005#1]
EN25F80 [DX0001]
EN25F80@SOP8(4.0) [DX1045#1]
EN25F80@SOP8(5.4) [DX1044#1]
EN25F80@VDFN8 [DX4005#1]
EN25LF05@SOP8(4.0) [DX1045#1]
EN25LF05@SOP8(5.4) [DX1044#1]
EN25LF05@VDFN8 [DX4005#1]
EN25LF10@SOP8(4.0) [DX1045#1]
EN25LF10@SOP8(5.4) [DX1044#1]
EN25LF10@VDFN8 [DX4005#1]
EN25LF20@SOP8 [DX1044#1]
EN25LF20@VDFN8 [DX4005#1]
EN25LF40 [DX0001]
EN25LF40@SOP8(150mil) [DX1045#1]
EN25LF40@SOP8(200mil) [DX1044#1]
EN25LF40@VDFN8 [DX4005#1]
EN25LV010@SOIC8 [DX1045]
EN25LV010@VFQFPN8 [DX4006]
EN25LV020@SOIC8 [DX1045#1]

EN25LV020@VFQFPN8 [DX4006#1]
EN25LV040@VFQFPN8 [DX4006#1]
EN25LV080@VFQFPN8 [DX4006#1]
EN25LV160@SOIC8(ISP) [DX0001]
EN25LV160@VFQFPN8(ISP) [DX0001]
EN25LV512@VFQFPN8 [DX4006]
EN25P05@SOP8(5.4) [DX1044]
EN25P10@SOP8(4.0) [DX1045]
EN25P10@VDFN8 [DX4005]
EN25P16@SOP8(ISP) [DX0001]
EN25P16@VFQFPN8(ISP) [DX0001]
EN25P20@SOP8(5.4) [DX1044#1]
EN25P32@SOP16 [DX1033#1]
EN25P32@SOP8 [DX1044#1]
EN25P32@VDFN8 [DX4006#1]
EN25P40@SOP8(4.0) [DX1045#1]
EN25P40@VDFN8 [DX4005#1]
EN25P64@SOP16(ISP) [DX1033#1]
EN25P64@VDFN8(ISP) [DX0001]
EN25P80@SOP8(5.4) [DX1044#1]
EN25Q128A [DX0001#1]
EN25Q128A@SOP8 [DX1044#1]
EN25Q128A@VSOP8 [DX1044#1]
EN25Q16@SOP16 [DX1072#1]
EN25Q16@SOP8(5.4) [DX1045#1]
EN25Q16A [DX0001]
EN25Q16A@SOP8(4.0) [DX1048#1]
EN25Q16A@VDFN8 [DX4006#1]
EN25Q32A@SOP8 [DX1044#1]
EN25Q32B [DX0001]
EN25Q32B@VDFN8 [DX4005#1]
EN25Q40@SOP8(5.4) [DX1045#1]
EN25Q40A@SOP8(4.0) [DX1044#1]
EN25Q40A@USON8 [DX4002#1]
EN25Q64@SOP16 [DX1033#1]
EN25Q64@VDFN8(5*6mm) [DX4005#1]
EN25Q80A@SOP8(4.0) [DX1045#1]
EN25Q80A@VDFN8 [DX4005#1]
EN25QA256@BGA24 [DX5146]
EN25QH128@SOP16 [DX1072#1]
EN25QH128@VDFN8 [DX4006#1]
EN25QH128A@SOP16 [DX1072#1]
EN25QH128A@TFBGA24 [DX5146]
EN25QH128A@VSOP8 [DX1044#1]
EN25QH256@TFBGA24 [DX5146]
EN25QH64@TFBGA24 [DX5146]
EN25QH64A@SOP16 [DX1033#1]
EN25QH64A@TFBGA24 [DX5146]
EN25LV040@SOIC8 [DX1045#1]
EN25LV080@SOIC8 [DX1045#1]
EN25LV160@SOIC8 [DX1045#1]
EN25LV160@VFQFPN8 [DX4006#1]
EN25LV512@SOIC8 [DX1045]
EN25P05@SOP8(4.0) [DX1045]
EN25P05@VDFN8 [DX4005]
EN25P10@SOP8(5.4) [DX1044]
EN25P16@SOP8 [DX1044#1]
EN25P16@VFQFPN8 [DX4006#1]
EN25P20@SOP8(4.0) [DX1045#1]
EN25P20@VDFN8 [DX4005#1]
EN25P32@SOP16(ISP) [DX0001]
EN25P32@SOP8(ISP) [DX0001]
EN25P32@VDFN8(ISP) [DX0001]
EN25P40@SOP8(5.4) [DX1044#1]
EN25P64@SOP16 [DX1033#1]
EN25P64@VDFN8 [DX4006#1]
EN25P80@SOP8(4.0) [DX1045#1]
EN25P80@VDFN8 [DX4005#1]
EN25Q128A@SOP16 [DX1072#1]
EN25Q128A@VDFN8 [DX4006#1]
EN25Q16 [DX0001]
EN25Q16@SOP8(4.0) [DX1044#1]
EN25Q16@VDFN8 [DX4006#1]
EN25Q16A@SOP16 [DX1072#1]
EN25Q16A@SOP8(5.4) [DX1044#1]
EN25Q32A [DX0001]
EN25Q32A@VDFN8 [DX4005#1]
EN25Q32B@SOP8 [DX1044#1]
EN25Q40@SOP8(4.0) [DX1044#1]
EN25Q40@VDFN8 [DX4005#1]
EN25Q40A@SOP8(5.4) [DX1045#1]
EN25Q40A@VDFN8 [DX4005#1]
EN25Q64@SOP8 [DX1044#1]
EN25Q64@VDFN8(6*8mm) [DX4006#1]
EN25Q80A@SOP8(5.4) [DX1044#1]
EN25QA128@TFBGA24 [DX5146]
EN25QA64@TFBGA24 [DX5146]
EN25QH128@TFBGA24 [DX5146]
EN25QH128A [DX0001#1]
EN25QH128A@SOP8 [DX1044#1]
EN25QH128A@VDFN8 [DX4006#1]
EN25QH256@SOP16 [DX1033#1]
EN25QH256@VDFN8 [DX4006#1]
EN25QH64A [DX0001]
EN25QH64A@SOP8 [DX1044#1]
EN25QH64A@VDFN8 [DX4005#1]

EN25S10@SOP8 [DX1045#1]
EN25S10@VDFN8 [DX4002#1]
EN25S16@SOP8 [DX1044#1]
EN25S16@VFQFPN8 [DX4006#1]
EN25S20@SOP8 [DX1045#1]
EN25S20@VDFN8 [DX4002#1]
EN25S32(Bottom Boot)@SOP16 [DX1033#1]
EN25S32(Bottom Boot)@SOP16(ISP) [DX1033#1]
EN25S32(Bottom Boot)@SOP8 [DX1044#1]
EN25S32(Bottom Boot)@SOP8(ISP) [DX0001]
EN25S32(Bottom Boot)@VDFN8 [DX4006#1]
EN25S32(Bottom Boot)@VDFN8(ISP) [DX0001]
EN25S32(Top Boot)@SOP16 [DX1033#1]
EN25S32(Top Boot)@SOP16(ISP) [DX1033#1]
EN25S32(Top Boot)@SOP8 [DX1044#1]
EN25S32(Top Boot)@SOP8(ISP) [DX0001]
EN25S32(Top Boot)@VDFN8 [DX4006#1]
EN25S32(Top Boot)@VDFN8(ISP) [DX0001]
EN25S32@SOP16 [DX1033#1]
EN25S32@SOP8 [DX1044#1]
EN25S32@VDFN8 [DX4006#1]
EN25S32@VSOP8 [DX1044#1]
EN25S40@SOP8 [DX1045#1]
EN25S40@VDFN8(2*3mm) [DX4002#1]
EN25S40@VDFN8(5*6mm) [DX4005#1]
EN25S64@VDFN8 [DX4005#1]
EN25S64@VSOP8 [DX1044#1]
EN25S80@SOP8(150mil) [DX1045]
EN25S80@SOP8(200mil) [DX1044]
EN25S80@VDFN8 [DX4005]
EN25T16@SOP8 [DX1044#1]
EN25T16@VFQFPN8 [DX4006#1]
EN25T40@SOP8(150mil) [DX1045#1]
EN25T40@SOP8(209mil) [DX1044#1]
EN25T40@VDFN8 [DX4005#1]
EN25T80 [DX0001]
EN25T80@SOP8 [DX1044#1]
EN25T80@VDFN8 [DX4005#1]
EN27C010 [DX0001]
EN27C010@PLCC32 [DX2032]
EN27C512 [DX0001]
EN27C512@PLCC32
EN27LN1G08@TSOP48 [DX1004-3]
EN29F002AB [DX0001]
EN29F002AB@PLCC32 [DX2032]
EN29F002AB@TSOP32 [DX1002]
EN29F002ANB [DX0001]
EN29F002ANB@PLCC32 [DX2032]
EN29F002ANB@TSOP32 [DX1002]
EN29F002ANT [DX0001]
EN29F002ANT@PLCC32 [DX2032]
EN29F002ANT@TSOP32 [DX1002]
EN29F002AT [DX0001]
EN29F002AT@PLCC32 [DX2032]
EN29F002AT@TSOP32 [DX1002]
EN29F002B [DX0001]
EN29F002B@PLCC32 [DX2032]
EN29F002B@TSOP32 [DX1002]
EN29F002NB [DX0001]
EN29F002NB@PLCC32 [DX2032]
EN29F002NB@TSOP32 [DX1002]
EN29F002NT [DX0001]
EN29F002NT@PLCC32 [DX2032]
EN29F002NT@TSOP32 [DX1002]
EN29F002T [DX0001]
EN29F002T@PLCC32 [DX2032]
EN29F002T@TSOP32 [DX1002]
EN29F010 [DX0001]
EN29F010@PLCC32 [DX2032]
EN29F010@TSOP32 [DX1002]
EN29F010@VSOP32 [DX1003]
EN29F040 [DX0001]
EN29F040@PLCC32 [DX2032]
EN29F040@TSOP32 [DX1002]
EN29F040A [DX0001]
EN29F040A@PLCC32 [DX2032]
EN29F040A@TSOP32 [DX1002]
EN29F080@TSOP40 [DX1006]
EN29F512 [DX0001]
EN29F512@PLCC32 [DX2032]
EN29F512@TSOP32 [DX1002]
EN29F512@VSOP32 [DX1003]
EN29F800B@TSOP48 [DX1004]
EN29F800T@TSOP48 [DX1004]

EN29LV010@PLCC32 [DX2032]
EN29LV010@TSOP32 [DX1002]
EN29LV010@VSOP32 [DX1003]
EN29LV010@WFBGA34 [DX5037]
EN29LV040@PLCC32 [DX2032]
EN29LV040@TSOP32 [DX1002]
EN29LV040@VSOP32 [DX1003]
EN29LV040A [DX0001]
EN29LV040A@PLCC32 [DX2032]
EN29LV040A@TSOP32 [DX1002]
EN29LV040A@VSOP32 [DX1003]
EN29LV160AB@FBGA48 [DX5002]
EN29LV160AB@TSOP48 [DX1004]
EN29LV160AT@FBGA48 [DX5002]
EN29LV160AT@TSOP48 [DX1004]
EN29LV160B@FBGA48 [DX5002]
EN29LV160B@TSOP48 [DX1004]
EN29LV160BB@FBGA48 [DX5002]
EN29LV160BB@TSOP48 [DX1004]
EN29LV160BT@FBGA48 [DX5002]
EN29LV160BT@TSOP48 [DX1004]
EN29LV160T@FBGA48 [DX5002]
EN29LV160T@TSOP48 [DX1004]
EN29LV320AB@FBGA48 [DX5002]
EN29LV320AB@TSOP48 [DX1004]
EN29LV320AT@FBGA48 [DX5002]
EN29LV320AT@TSOP48 [DX1004]
EN29LV320B@FBGA48 [DX5002]
EN29LV320B@TSOP48 [DX1004]
EN29LV320T@FBGA48 [DX5002]
EN29LV320T@TSOP48 [DX1004]
EN29LV400AB@FBGA48 [DX5002]
EN29LV400AB@TSOP48 [DX1004]
EN29LV400AT@FBGA48 [DX5002]
EN29LV400AT@TSOP48 [DX1004]
EN29LV400B@FBGA48 [DX5002]
EN29LV400B@TSOP48 [DX1004]
EN29LV400T@FBGA48 [DX5002]
EN29LV400T@TSOP48 [DX1004]
EN29LV512@PLCC32 [DX2032]
EN29LV512@TSOP32 [DX1002]
EN29LV512@VSOP32 [DX1003]
EN29LV640B@FBGA48 [DX5002]
EN29LV640B@TSOP48 [DX1004]
EN29LV640H@FBGA48 [DX5002]
EN29LV640H@TSOP48 [DX1004]
EN29LV640L@FBGA48 [DX5002]
EN29LV640L@TSOP48 [DX1004]
EN29LV640T@FBGA48 [DX5002]
EN29LV640T@TSOP48 [DX1004]
EN29LV641H@FBGA63 [DX5041]
EN29LV641H@TSOP48 [DX1004]
EN29LV641L@FBGA63 [DX5041]
EN29LV641L@TSOP48 [DX1004]
EN29LV800AB@FBGA48 [DX5002]
EN29LV800AB@TSOP48 [DX1004]
EN29LV800AT@FBGA48 [DX5002]
EN29LV800AT@TSOP48 [DX1004]
EN29LV800B@TSOP48 [DX1004]
EN29LV800BB@FBGA48 [DX5002]
EN29LV800BB@TSOP48 [DX1004]
EN29LV800BT@FBGA48 [DX5002]
EN29LV800BT@TSOP48 [DX1004]
EN29LV800CB@FBGA48 [DX5002]
EN29LV800CB@TSOP48 [DX1004]
EN29LV800CT@FBGA48 [DX5002]
EN29LV800CT@TSOP48 [DX1004]
EN29LV800T@TSOP48 [DX1004]
EN29PL032@FBGA48 [DX5002]
EN29PL032@FBGA56 [DX5045]
EN29PL032@TSOP48 [DX1004]
EN29PL064@FBGA48 [DX5002]
EN29PL064@FBGA56 [DX5045]
EN29PL064@TSOP48 [DX1004]
EN29SL160B@FBGA48 [DX5002]
EN29SL160B@TSOP48 [DX1004]
EN29SL160B@WFBGA48 [DX5038]
EN29SL160B@WLGA48 [DX5038]
EN29SL160T@FBGA48 [DX5002]
EN29SL160T@TSOP48 [DX1004]
EN29SL160T@WFBGA48 [DX5038]
EN29SL160T@WLGA48 [DX5038]
EN29SL400B@FBGA48 [DX5002]
EN29SL400B@TSOP48 [DX1004]
EN29SL400T@FBGA48 [DX5002]
EN29SL400T@TSOP48 [DX1004]
EN29SL800B@FBGA48 [DX5002]
EN29SL800B@TSOP48 [DX1004]
EN29SL800B@WFBGA48 [DX5038]
EN29SL800B@WLGA48 [DX5038]
EN29SL800T@FBGA48 [DX5002]
EN29SL800T@TSOP48 [DX1004]
EN29SL800T@WFBGA48 [DX5038]
EN29SL800T@WLGA48 [DX5038]
EN71PL03280@FBGA56 [DX5045]
EN71PL032A0@FBGA56 [DX5045]

EN71PL064A0@FBGA56 [DX5045]
EN71PL064B0@FBGA56 [DX5045]

EON-CUSTOMER

E(E)PROM/FRAM/NVRAM

EN27LN1G08(B0NBB)@TSOP48 [DX1004-3]
EN27LN2G08(B0NBB)@TSOP48 [DX1004-3]

EOREX

E(E)PROM/FRAM/NVRAM

EM24LC02@SOP8 [DX1045]

EPSON

E(E)PROM/FRAM/NVRAM

S1H0H324B2B1@FBGA66 [DX5026]
S1H0H324B2T1@FBGA66 [DX5026]
S1H0H326B2B1@FBGA66 [DX5026]
S1H0H326B2T1@FBGA66 [DX5026]
S1H0H328B2B2@FBGA66 [DX5026]
S1H0H328B2T2@FBGA66 [DX5026]
S1H0J642B2B3@FBGA68 [DX5026]
S1H0J642B2T3@FBGA68 [DX5026]
S1H0J646B2B3@FBGA68 [DX5026]
S1H0J646B2T3@FBGA68 [DX5026]
S1H0J648B2B2@FBGA68 [DX5026]
S1H0J648B2T2@FBGA68 [DX5026]

ESIGMA

E(E)PROM/FRAM/NVRAM

ES27LN1G08@TSOP48 [DX1004-3]

ESMT

E(E)PROM/FRAM/NVRAM

EM25LV010@SOIC8 [DX1045]
EM25LV010@VFQFPN8 [DX4006]
EM25LV512@SOIC8 [DX1045]
EM25LV512@VFQFPN8 [DX4006]
F25D04QA@SOIC8 [DX1045#1]
F25D04QA@WSON8 [DX4005#1]
F25D08QA@SOIC8(150mil) [DX1045#1]
F25D08QA@SOIC8(200mil) [DX1044#1]
F25D08QA@WSON8 [DX4005#1]
F25D64QA@SOIC8 [DX1044#1]
F25D64QA@WSON8 [DX4005]
F25L004AB [DX0001]
F25L004AB@SOIC8(150mil) [DX1045]
F25L004AB@SOIC8(200mil) [DX1044]

F25L004AT [DX0001]
F25L004AT@SOIC8(150mil) [DX1045]
F25L004AT@SOIC8(200mil) [DX1044]
F25L008AB@SOIC8 [DX1044]
F25L008AT@SOIC8 [DX1044]
F25L016AB@SOIC8 [DX1044]
F25L016AT@SOIC8 [DX1044]
F25L01PA [DX0001]
F25L01PA(2D)@SOIC8 [DX1045#1]
F25L01PA(2D)@TSSOP8 [DX1059#3]
F25L01PA@SOIC8(150mil) [DX1045#1]
F25L01PA@SOIC8(200mil) [DX1044#1]
F25L02PA [DX0001]
F25L02PA(2F)@SOIC8(150mil) [DX1045#1]
F25L02PA(2F)@SOIC8(200mil) [DX1044#1]
F25L02PA(2F)@WSON8 [DX4005#1]
F25L02PA@SOIC8(150mil) [DX1045#1]
F25L02PA@SOIC8(200mil) [DX1044#1]
F25L04PA [DX0001]
F25L04PA@SOIC8(150mil) [DX1045#1]
F25L04PA@SOIC8(200mil) [DX1044#1]
F25L05PA(2D)@SOIC8 [DX1045#1]
F25L05PA(2D)@TSSOP8 [DX1059#3]
F25L08PA(2G) [DX0001]
F25L08PA(2G)@SOIC8(150mil) [DX1045]
F25L08PA(2G)@SOIC8(200mil) [DX1044]
F25L08PA(2G)@WSON8 [DX4005]
F25L08PA(AAI-PROGRAM)@SOIC8 [DX1044]
F25L08PA(PAGE-PROGRAM)@SOIC8 [DX1044]
F25L08QA(2S)@SOIC8(150mil) [DX1045#1]
F25L08QA(2S)@SOIC8(200mil) [DX1044#1]
F25L08QA@SOIC8(150mil) [DX1045#1]
F25L08QA@SOIC8(200mil) [DX1044#1]
F25L16PA(2S) [DX0001]
F25L16PA(2S)@SOIC8(150mil) [DX1045#1]
F25L16PA(2S)@SOIC8(200mil) [DX1044#1]
F25L16PA(2S)@SOICS16 [DX1033#1]
F25L16PA(2S)@WSON08 [DX4005]
F25L16PA(AAI-PROGRAM)@SOIC8 [DX1044]
F25L16PA(PAGE-PROGRAM)@SOIC8 [DX1044]
F25L16QA [DX0001]
F25L16QA@SOIC16 [DX1033#1]
F25L16QA@SOIC8(150mil) [DX1045]
F25L16QA@SOIC8(200mil) [DX1044]
F25L16QA@WSON8 [DX4005]
F25L320PA(4K OTP)@SOIC16 [DX1033#1]
F25L320PA(4K OTP)@SOIC8 [DX1044#1]
F25L320PA@SOIC16 [DX1033#1]
F25L320PA@SOIC8 [DX1044#1]
F25L32PA(4K OTP)(new)@SOIC16 [DX1033#1]
F25L32PA(4K OTP)(new)@SOIC8 [DX1044#1]
F25L32PA(4K OTP)@SOIC16 [DX1033#1]
F25L32PA(4K OTP)@SOIC8 [DX1044#1]
F25L32PA(new)@SOIC16 [DX1033#1]
F25L32PA(new)@SOIC8 [DX1044#1]
F25L32PA@SOIC16 [DX1033#1]
F25L32PA@SOIC8 [DX1044#1]
F25L32QA(2S)@SOIC16 [DX1033#1]
F25L32QA(2S)@SOIC8 [DX1044#1]
F25L32QA(2S)@WSON8 [DX4005]
F25L32QA(4K OTP)@SOIC16 [DX1033#1]

F25L32QA(4K OTP)@SOIC8 [DX1044#1]
F25L32QA@SOIC16 [DX1033#1]
F25L32QA@SOIC8 [DX1044#1]
F25L64QA@BGA24 [DX5146]
F25L64QA@SOIC16 [DX1033#1]
F25L64QA@SOIC8 [DX1044#1]
F25L64QA@WSON8 [DX4005]
F29L064BGA@TSOP48 [DX1004]
F29L064UGA@TSOP48 [DX1004]
F49B002UA [DX0001]
F49B002UA@PLCC32 [DX2032]
F49L004BA@PLCC32 [DX2032]
F49L004BA@TSOP40 [DX1006]
F49L004UA@PLCC32 [DX2032]
F49L004UA@TSOP40 [DX1006]
F49L040A@PLCC32 [DX2032]
F49L040A@VSOP32 [DX1003]
F49L160BA@TSOP48 [DX1004]
F49L160UA@TSOP48 [DX1004]
F49L320BA@TSOP48 [DX1004]
F49L320UA@TSOP48 [DX1004]
F49L400BA@TSOP48 [DX1004]
F49L400UA@TSOP48 [DX1004]
F49L800BA@TSOP48 [DX1004]
F49L800UA@TSOP48 [DX1004]
F50L1G41A@WSON8
F50L512M41A@WSON8
F59D1G81A@BGA63 [DX5046-1]
F59D1G81A@TSOP48 [DX1004-3]
F59D2G81A@BGA63 [DX5046-1]
F59D2G81A@TSOP48 [DX1004-3]
F59D4G81A@TSOP48 [DX1004-3]
F59L1G81A@BGA63 [DX5046-1]
F59L1G81A@TSOP48 [DX1004-3]
F59L1G81LA@TSOP48 [DX1004-3]
F59L1G81MA@TSOP48 [DX1004-3]
F59L2G81A@BGA63 [DX5046-1]
F59L2G81A@TSOP48 [DX1004-3]
F59L4G81A@TSOP48 [DX1004-3]
F59L512M81A@TSOP48 [DX1004-3]
FM60D1G12A@BGA107 [DX5028]
FM60D1G56A@BGA107 [DX5028]
FM61D1G12A@BGA107 [DX5028]
FM64D1G12A@BGA130 [DX5140-1]
FM64D1G12MA@BGA130 [DX5028-1]
FM64D1G56A@BGA130 [DX5140-1]
FM67D2G1GA@BGA137 [DX5011-1]
FM67D4G2GA@BGA130 [DX5011-1]
FM69D1G56A@BGA137 [DX5011-1]
FM6AD1G12A@BGA130 [DX5011-1]
FM6AD1G12MA@BGA130 [DX5011-1]
FM6AD2G1GA@BGA137 [DX5011-1]
FM6AD4G2GA@BGA137 [DX5011-1]
FM91D06432BNA@FBGA56 [DX5045]
FM91D06432UNA@FBGA56 [DX5045]
FM91L01604BA@FBGA56 [DX5045]
FM91L01604UA@FBGA56 [DX5045]
FM91L03204BA@FBGA56 [DX5045]
FM91L03204UA@FBGA56 [DX5045]
FM91L03208BA@FBGA56 [DX5045]
FM91L03208BIA@FBGA56 [DX5045]
FM91L03208UA@FBGA56 [DX5045]
FM91L03208UIA@FBGA56 [DX5045]
FM91L03216BA@FBGA56 [DX5045]
FM91L03216UA@FBGA56 [DX5045]

ESMT-CUSTOMER

E(E)PROM/FRAM/NVRAM

F59L1G81A(REALTEK)@TSOP48 [DX1004-1]

ESTEK

E(E)PROM/FRAM/NVRAM

24C02 [DX0001]
24C02@SOP8 [DX1045]
24C02@TSSOP8 [DX1059]
24C04 [DX0001]

24C04@SOP8 [DX1045]
24C04@TSSOP8 [DX1059]
24C08 [DX0001]
24C08@SOP8 [DX1045]
24C08@TSSOP8 [DX1059]
24C16 [DX0001]
24C16@SOP8 [DX1045]
24C16@TSSOP8 [DX1059]
K24C32 [DX0001]
K24C32@SOP8 [DX1045]
K24C32@TSSOP8 [DX1059]
K24C64 [DX0001]
K24C64@SOP8 [DX1045]
K24C64@TSSOP8 [DX1059]

E-TRAND

E(E)PROM/FRAM/NVRAM

AMI29DL163BT@TSOP48 [DX1004]
AMI29DL163TT@TSOP48 [DX1004]

EVERSPIN

E(E)PROM/FRAM/NVRAM

M24A16B@FBGA48 [DX5085]
M24A16B@TSOP44 [DX1046]
MR0A08B@FBGA48 [DX5085]
MR0A08B@SOIC32 [DX1069]
MR0A08B@TSOP44 [DX1046]
MR0A16A@FBGA48 [DX5085]
MR0A16A@TSOP44 [DX1046]
MR0A16B@FBGA48 [DX5085]
MR0A16B@TSOP44 [DX1046]
MR0D08B@FBGA48 [DX5085]
MR0DL08B@FBGA48 [DX5085]
MR10Q010@SOIC16 [DX1072#1]
MR20H40CDC [DX4005#1]
MR20H40CDCR [DX4005#1]
MR20H40CPU [DX0001]
MR20H40MDC [DX4005#1]
MR20H40MDCR [DX4005#1]
MR20H40MPU [DX0001]
MR256A08@FBGA48 [DX5085]
MR256A08@SOIC32 [DX1069]
MR256A08@TSOP44 [DX1046]
MR256A08B@FBGA48 [DX5085]
MR256A08B@SOIC32 [DX1069]
MR256A08B@TSOP44 [DX1046]
MR256D08B@FBGA48 [DX5085]
MR25H10CDC [DX4005#1]
MR25H10CDCR [DX4005#1]
MR25H10MDC [DX4005#1]
MR25H10MDCR [DX4005#1]
MR25H256CDC [DX4005#1]
MR25H256CDCR [DX4005#1]
MR25H256MDC [DX4005#1]
MR25H256MDCR [DX4005#1]
MR25H40CDC [DX4005#1]
MR25H40CDCR [DX4005#1]
MR25H40CPU [DX0001]
MR25H40MDC [DX4005#1]
MR25H40MDCR [DX4005#1]
MR25H40MPU [DX0001]
MR2A08A@FBGA48 [DX5085]
MR2A08A@TSOP44 [DX1046]
MR2A16A@FBGA48 [DX5085]
MR2A16A@TSOP44 [DX1046]
MR4A08B@FBGA48 [DX5085]
MR4A08B@TSOP44 [DX1046]
MR4A16B@FBGA48 [DX5085]
MR4A16B@TSOP48 [DX1007]
MR4A16B@TSOP54 [DX1010]

EVERSTAR

E(E)PROM/FRAM/NVRAM

EV29LV160AB [DX0001]
EV29LV160AT [DX0001]
EV29LV640MB [DX0001]
EV29LV640MT [DX0001]

EXAR

MICROCONTROLLER

XPR7708ILB [DX4017-1]
XPR7714ILB [DX4017-1]
XPR7740ILB [DX4017-1]
XRP7708ILB [DX4017-1]
XRP7708ILB(HEX) [DX4017-1]
XRP7714ILB [DX4017-1]
XRP7714ILB(HEX) [DX4017-1]
XRP7724ILB@QFN44 [DX4018]
XRP7740ILB [DX4017-1]
XRP7740ILB(HEX) [DX4017-1]
XRP9710ILB [DX5262]
XRP9711ILB [DX5262]

EXCELSEMI

E(E)PROM/FRAM/NVRAM

ES25M16 [DX0001]
ES25M16@SOP16 [DX1033#1]
ES25M16@SOP8[150 mil] [DX1044#1]
ES25M16@SOP8[208 mil] [DX1045#1]
ES25M40 [DX0001]
ES25M40@SOP16 [DX1033#1]
ES25M40@SOP8[150 mil] [DX1044#1]
ES25M40@SOP8[208 mil] [DX1045#1]
ES25M80 [DX0001]
ES25M80@SOP16 [DX1033#1]
ES25M80@SOP8[150 mil] [DX1044#1]
ES25M80@SOP8[208 mil] [DX1045#1]
ES25P16@SOP8 [DX1044#1]
ES25P40@SOP8 [DX1044#1]
ES25P80@SOP8 [DX1044#1]
ES29LV160DB@FBGA48 [DX5002]
ES29LV160DB@PSOP44 [DX1014]
ES29LV160DB@TSOP48 [DX1004]
ES29LV160DT@FBGA48 [DX5002]
ES29LV160DT@PSOP44 [DX1014]
ES29LV160DT@TSOP48 [DX1004]
ES29LV160EB@FBGA48 [DX5002]
ES29LV160EB@TSOP48 [DX1004]
ES29LV160ET@FBGA48 [DX5002]
ES29LV160ET@TSOP48 [DX1004]
ES29LV160FB@FBGA48 [DX5002]
ES29LV160FB@TSOP48 [DX1004]
ES29LV160FT@FBGA48 [DX5002]
ES29LV160FT@TSOP48 [DX1004]
ES29LV320DB@FBGA48 [DX5022]
ES29LV320DB@TSOP48 [DX1004]
ES29LV320DT@FBGA48 [DX5022]
ES29LV320DT@TSOP48 [DX1004]
ES29LV320EB@FBGA48 [DX5002]
ES29LV320EB@TSOP48 [DX1004]
ES29LV320ET@FBGA48 [DX5002]
ES29LV320ET@TSOP48 [DX1004]
ES29LV320FB@FBGA48 [DX5002]
ES29LV320FB@TSOP48 [DX1004]
ES29LV320FT@FBGA48 [DX5002]
ES29LV320FT@TSOP48 [DX1004]
ES29LV400DB@FBGA48 [DX5002]
ES29LV400DB@TSOP48 [DX1004]
ES29LV400DT@FBGA48 [DX5002]
ES29LV400DT@TSOP48 [DX1004]
ES29LV400EB@FBGA48 [DX5002]
ES29LV400EB@TSOP48 [DX1004]
ES29LV400ET@FBGA48 [DX5002]
ES29LV400ET@TSOP48 [DX1004]
ES29LV800DB@FBGA48 [DX5002]
ES29LV800DB@PSOP44 [DX1014]
ES29LV800DB@TSOP48 [DX1004]

ES29LV800DT@FBGA48 [DX5002]
ES29LV800DT@PSOP44 [DX1014]
ES29LV800DT@TSOP48 [DX1004]
ES29LV800EB@FBGA48 [DX5002]
ES29LV800EB@TSOP48 [DX1004]
ES29LV800ET@FBGA48 [DX5002]
ES29LV800ET@TSOP48 [DX1004]

EXEL

E(E)PROM/FRAM/NVRAM

XL24C01A [DX0001]
XL24C02 [DX0001]
XL24C04 [DX0001]
XL24C16 [DX0001]
XL24C16@SOIC8 [DX1045]
XL24C32 [DX0001]
XL28C256 [DX0001]
XL28C256@PLCC32 [DX2032]
XL28C256@TSOP28 [DX1024]
XL9010 [DX0001]
XL9010(F) [DX1045]
XL9020 [DX0001]
XL9020(F) [DX1045]
XL9040 [DX0001]
XL9040(F) [DX1045]
XL9346 [DX0001]
XL9346@SOIC8 [DX1045]
XL93CS56 [DX0001]
XL93CS56@SOIC8 [DX1045]
XL93CS56@TSSOP8 [DX1059]
XL93CS66 [DX0001]
XL93CS66@SOIC8 [DX1045]
XL93CS66@TSSOP8 [DX1059]
XL93LC46 [DX0001]
XL93LC46@SOIC8 [DX1045]
XL93LC46A [DX0001]
XL93LC46A@SOIC8 [DX1045]
XL93LC56 [DX0001]
XL93LC56@SOIC8 [DX1045]
XL93LC56A [DX0001]
XL93LC56A@SOIC8 [DX1045]
XL93LC66A [DX0001]
XL93LC66A@SOIC8 [DX1045]
XL9764 [DX0001]
XLE28C16A [DX0001]
XLE28C16A@PLCC32 [DX2032]
XLE28C16B [DX0001]
XLE28C16B@PLCC32 [DX2032]
XLE28C16B@SOIC24 [DX1033]
XLM28C16A [DX0001]
XLM28C16A@PLCC32 [DX2032]
XLM46C15 [DX0001]
XLM46P15 [DX0001]
XLS2804A [DX0001]
XLS2816A [DX0001]
XLS2816A@PLCC32 [DX2032]
XLS2817A [DX0001]
XLS28C16A [DX0001]
XLS28C16A@PLCC32 [DX2032]
XLS28C16B [DX0001]
XLS28C16B@PLCC32 [DX2032]
XLS28C16B@SOIC24 [DX1033]
XLS28C64B [DX0001]
XLS28C64B@PLCC32 [DX2032]
XLS28C64B@SOIC28 [DX1033]
XLS46C15 [DX0001]
XLS46P15 [DX0001]
XLS93C46 [DX0001]
XLS93C46@SOIC8 [DX1045]
XLS93C56 [DX0001]
XLS93C56@SOIC8 [DX1045]
XLS93C66 [DX0001]
XLS93C66@SOIC8 [DX1045]
XLS93CS46 [DX0001]
XLS93CS46@SOIC8 [DX1045]
XLS93CS46@TSSOP8 [DX1059]
XLS93LC06 [DX0001]
XLS93LC06@SOIC8 [DX1045]
XLS93LC66 [DX0001]
XLS93LC66@SOIC8 [DX1045]

EXPLORE

MICROCONTROLLER

EP94M1R [DX4021-3]
EP94Z1E@QFP64 [DX3085-2]
EP94Z3E@QFP80 [DX3131-1]
EPF011A [DX3057-11]
EPF011C [DX1025-1]
EPF011D [DX3127]
EPF021A@QFP64 [DX3085-1]
EPF021D@QFP48 [DX3127]
EPF025A@QFP64 [DX3085-1]
EPF025R [DX3085-1]

FAIRCHILD

E(E)PROM/FRAM/NVRAM

FM24C02(M8)@SOIC8 [DX1045]
FM24C02(MT8)@TSSOP8 [DX1059]
FM24C02(N) [DX0001]
FM24C03(M8)@SOIC8 [DX1045]
FM24C03(MT8)@TSSOP8 [DX1059]
FM24C03(N) [DX0001]
FM24C04(M8)@SOIC8 [DX1045]
FM24C04(MT8)@TSSOP8 [DX1059]
FM24C04(N) [DX0001]
FM24C05(M8)@SOIC8 [DX1045]
FM24C05(MT8)@TSSOP8 [DX1059]
FM24C05(N) [DX0001]
FM24C08(M8)@SOIC8 [DX1045]
FM24C08(MT8)@TSSOP8 [DX1059]
FM24C08(N) [DX0001]
FM24C09(M8)@SOIC8 [DX1045]
FM24C09(MT8)@TSSOP8 [DX1059]
FM24C09(N) [DX0001]
FM24C128(MT8)@TSSOP8 [DX1059]
FM24C128(MW8)@SOIC8 [DX1045]
FM24C128(N) [DX0001]
FM24C16(M8)@SOIC8 [DX1045]
FM24C16(MT8)@TSSOP8 [DX1059]
FM24C16(N) [DX0001]
FM24C17(M8)@SOIC8 [DX1045]
FM24C17(MT8)@TSSOP8 [DX1059]
FM24C17(N) [DX0001]
FM24C256(M8)@SOIC8 [DX1045]
FM24C256(N) [DX0001]
FM24C32(M8)@SOIC8 [DX1045]
FM24C32(N) [DX0001]
FM27C010 [DX0001]
FM27C010@PLCC32 [DX2032]
FM27C010@TSOP32 [DX1002]
FM27C040 [DX0001]
FM27C040@PLCC32 [DX2032]
FM27C040@TSOP32 [DX1002]
FM27C256 [DX0001]
FM27C256@PLCC32 [DX2032]
FM27C256Q [DX0001]
FM27C256Q@PLCC32 [DX2032]
FM27C512 [DX0001]
FM27C512@PLCC32 [DX2032]
FM93C06(M8)(08bit)@SOIC8 [DX1045]
FM93C06(M8)(16bit)@SOIC8 [DX1045]
FM93C06(MT8)(08bit)@TSSOP8 [DX1059]
FM93C06(MT8)(16bit)@TSSOP8 [DX1059]
FM93C06(N)(08bit) [DX0001]
FM93C06(N)(16bit) [DX0001]
FM93C14(16bit) [DX0001]
FM93C46(M8)@SOIC8 [DX1045]
FM93C46(MT8)@TSSOP8 [DX1059]
FM93C46(N) [DX0001]
FM93C46A(M8)(08bit)@SOIC8 [DX1045]
FM93C46A(M8)(16bit)@SOIC8 [DX1045]
FM93C46A(MT8)(08bit)@TSSOP8 [DX1059]
FM93C46A(MT8)(16bit)@TSSOP8 [DX1059]
FM93C46A(N)(08bit) [DX0001]
FM93C46A(N)(16bit) [DX0001]

FM93C56(M8)@SOIC8 [DX1045]
FM93C56(MT8)@TSSOP8 [DX1059]
FM93C56(N) [DX0001]
FM93C56A(M8)(08bit)@SOIC8 [DX1045]
FM93C56A(M8)(16bit)@SOIC8 [DX1045]
FM93C56A(MT8)(08bit)@TSSOP8 [DX1059]
FM93C56A(MT8)(16bit)@TSSOP8 [DX1059]
FM93C56A(N)(08bit) [DX0001]
FM93C56A(N)(16bit) [DX0001]
FM93C66(M8)@SOIC8 [DX1045]
FM93C66(MT8)@TSSOP8 [DX1059]
FM93C66(N) [DX0001]
FM93C66A(M8)(08bit)@SOIC8 [DX1045]
FM93C66A(M8)(16bit)@SOIC8 [DX1045]
FM93C66A(MT8)(08bit)@TSSOP8 [DX1059]
FM93C66A(MT8)(16bit)@TSSOP8 [DX1059]
FM93C66A(N)(08bit) [DX0001]
FM93C66A(N)(16bit) [DX0001]
FM93C76(M8)(16bit)@SOIC8 [DX1045]
FM93C76(MT8)(16bit)@TSSOP8 [DX1059]
FM93C76(N)(16bit) [DX0001]
FM93C76A(M8)(08bit)@SOIC8 [DX1045]
FM93C76A(M8)(16bit)@SOIC8 [DX1045]
FM93C76A(MT8)(08bit)@TSSOP8 [DX1059]
FM93C76A(MT8)(16bit)@TSSOP8 [DX1059]
FM93C76A(N)(08bit) [DX0001]
FM93C76A(N)(16bit) [DX0001]
FM93C86(M8)(16bit)@SOIC8 [DX1045]
FM93C86(MT8)(16bit)@TSSOP8 [DX1059]
FM93C86(N)(16bit) [DX0001]
FM93C86A(M8)(08bit)@SOIC8 [DX1045]
FM93C86A(M8)(16bit)@SOIC8 [DX1045]
FM93C86A(MT8)(08bit)@TSSOP8 [DX1059]
FM93C86A(MT8)(16bit)@TSSOP8 [DX1059]
FM93C86A(N)(08bit) [DX0001]
FM93C86A(N)(16bit) [DX0001]
FM93CS06(M8)@SOIC8 [DX1045]
FM93CS06(MT8)@TSSOP8 [DX1059]
FM93CS06(N) [DX0001]
FM93CS46(M8)@SOIC8 [DX1045]
FM93CS46(MT8)@TSSOP8 [DX1059]
FM93CS46(N) [DX0001]
FM93CS56(M8)@SOIC8 [DX1045]
FM93CS56(MT8)@TSSOP8 [DX1059]
FM93CS56(N) [DX0001]
FM93CS66(M8)@SOIC8 [DX1045]
FM93CS66(MT8)@TSSOP8 [DX1059]
FM93CS66(N) [DX0001]
FM93S46(M8)@SOIC8 [DX1045]
FM93S46(MT8)@TSSOP8 [DX1059]
FM93S46(N) [DX0001]
FM93S56(M8)@SOIC8 [DX1045]
FM93S56(MT8)@TSSOP8 [DX1059]
FM93S56(N) [DX0001]
FM93S66(M8)@SOIC8 [DX1045]
FM93S66(MT8)@TSSOP8 [DX1059]
FM93S66(N) [DX0001]
MM2716 [DX0001]
MM2716E [DX0001]
NM24C02(M8)@SOIC8 [DX1045]
NM24C02(MT8)@TSSOP8 [DX1059]
NM24C02(N) [DX0001]
NM24C02L(M8)@SOIC8 [DX1045]
NM24C02L(MT8)@TSSOP8 [DX1059]
NM24C02L(N) [DX0001]
NM24C03(M8)@SOIC8 [DX1045]
NM24C03(MT8)@TSSOP8 [DX1059]
NM24C03(N) [DX0001]
NM24C04(M8)@SOIC8 [DX1045]
NM24C04(MT8)@TSSOP8 [DX1059]
NM24C04(N) [DX0001]
NM24C05(M8)@SOIC8 [DX1045]

NM24C05(MT8)@TSSOP8 [DX1059]
NM24C05(N) [DX0001]
NM24C08(M8)@SOIC8 [DX1045]
NM24C08(MT8)@TSSOP8 [DX1059]
NM24C08(N) [DX0001]
NM24C09(M8)@SOIC8 [DX1045]
NM24C09(MT8)@TSSOP8 [DX1059]
NM24C09(N) [DX0001]
NM24C16(M8)@SOIC8 [DX1045]
NM24C16(MT8)@TSSOP8 [DX1059]
NM24C16(N) [DX0001]
NM24C17(M8)@SOIC8 [DX1045]
NM24C17(MT8)@TSSOP8 [DX1059]
NM24C17(N) [DX0001]
NM24C65(M8)SOIC8 [DX1045]
NM24C65(N) [DX0001]
NM27C010 [DX0001]
NM27C010@PLCC32 [DX2032]
NM27C010@TSOP32 [DX1002]
NM27C020 [DX0001]
NM27C020@PLCC32 [DX2032]
NM27C020@TSOP32 [DX1002]
NM27C020Q [DX0001]
NM27C020Q@PLCC32 [DX2032]
NM27C020Q@TSOP32 [DX1002]
NM27C040 [DX0001]
NM27C040@PLCC32 [DX2032]
NM27C040@TSOP32 [DX1002]
NM27C128 [DX0001]
NM27C128@PLCC32 [DX2032]
NM27C210 [DX0001]
NM27C210@PLCC44 [DX2044]
NM27C240 [DX0001]
NM27C240@PLCC44 [DX2044]
NM27C256 [DX0001]
NM27C256@PLCC32 [DX2032]
NM27C512 [DX0001]
NM27C512@PLCC32 [DX2032]
NM27C64Q [DX0001]
NM27C64Q@PLCC32 [DX2032]
NM27LC256 [DX0001]
NM27LC256@PLCC32 [DX2032]
NM27LC512 [DX0001]
NM27LC512@PLCC32 [DX2032]
NM27LV010 [DX0001]
NM27LV010@PLCC32 [DX2032]
NM27LV010@TSOP32 [DX1002]
NM27LV210 [DX0001]
NM27LV210@PLCC44 [DX2044]
NM27LV512 [DX0001]
NM27LV512@PLCC32 [DX2032]
NM27P040 [DX0001]
NM27P040@PLCC32 [DX2032]
NM27P040@TSOP32 [DX1002]
NM27P210 [DX0001]
NM27P210@PLCC44 [DX2044]
NM27P512 [DX0001]
NM27P512@PLCC32 [DX2032]
NM93C66(M8)(16bit)@SOIC8 [DX1045]
NM93C66(MT8)(16bit)@TSSOP8 [DX1059]
NM93C66(N)(16bit) [DX0001]
NM93CS06(M8)@SOIC8 [DX1045]
NM93CS06(MT8)@TSSOP8 [DX1059]
NM93CS06(N) [DX0001]
NM93CS46(M8)@SOIC8 [DX1045]
NM93CS46(MT8)@TSSOP8 [DX1059]
NM93CS46(N) [DX0001]
NM93CS56(M8)@SOIC8 [DX1045]
NM93CS56(MT8)@TSSOP8 [DX1059]
NM93CS56(N) [DX0001]
NM93CS66(M8)@SOIC8 [DX1045]
NM93CS66(MT8)@TSSOP8 [DX1059]
NM93CS66(N) [DX0001]
NMC2732 [DX0001]
NMC27C010 [DX0001]
NMC27C010@PLCC32 [DX2032]
NMC27C010@TSOP32 [DX1002]
NMC27C1024 [DX0001]
NMC27C1024@PLCC44 [DX2044]
NMC27C128B [DX0001]
NMC27C128B@PLCC32 [DX2032]
NMC27C128BN [DX0001]
NMC27C128BN@PLCC32 [DX2032]
NMC27C128BQ [DX0001]
NMC27C128BQ@PLCC32 [DX2032]
NMC27C128CQ [DX0001]
NMC27C16 [DX0001]
NMC27C16BQ [DX0001]
NMC27C16BQE [DX0001]
NMC27C16H [DX0001]
NMC27C16HQ [DX0001]
NMC27C16Q [DX0001]
NMC27C256 [DX0001]
NMC27C256@PLCC32 [DX2032]

NMC27C256B [DX0001]
NMC27C256B@PLCC32 [DX2032]
NMC27C256Q [DX0001]
NMC27C256Q@PLCC32 [DX2032]
NMC27C32 [DX0001]
NMC27C32B [DX0001]
NMC27C32BQ [DX0001]
NMC27C32E [DX0001]
NMC27C32EH [DX0001]
NMC27C32H [DX0001]
NMC27C512 [DX0001]
NMC27C512@PLCC32 [DX2032]
NMC27C512A [DX0001]
NMC27C512A@PLCC32 [DX2032]
NMC27C512AN [DX0001]
NMC27C512AN@PLCC32 [DX2032]
NMC27C64 [DX0001]
NMC27C64(BN) [DX0001]
NMC27C64(N) [DX0001]
NMC27CP128 [DX0001]
NMC87C257Q [DX0001]
NMC87C257Q@PLCC32 [DX2032]
NMC87C257V [DX0001]
NMC87C257V@PLCC32 [DX2032]
NMC9346(M8)(16bit)@SOIC8 [DX1045]
NMC9346(MT8)(16bit)@TSSOP8 [DX1059]
NMC9346(N)(16bit) [DX0001]
NMC93C46(M8)(16bit)@SOIC8 [DX1045]
NMC93C46(MT8)(16bit)@TSSOP8 [DX1059]
NMC93C46(N)(16bit) [DX0001]
NMC93C46A(M8)(16bit)@SOIC8 [DX1045]
NMC93C46A(MT8)(16bit)@TSSOP8 [DX1059]
NMC93C46A(N)(16bit) [DX0001]
NMC93C56(M8)(16bit)@SOIC8 [DX1045]
NMC93C56(MT8)(16bit)@TSSOP8 [DX1059]
NMC93C56(N)(16bit) [DX0001]
NMC93C66(M8)(16bit)@SOIC8 [DX1045]
NMC93C66(MT8)(16bit)@TSSOP8 [DX1059]
NMC93C66(N)(16bit) [DX0001]
NMC93CS06(M8)@SOIC8 [DX1045]
NMC93CS06(MT8)@TSSOP8 [DX1059]
NMC93CS06(N) [DX0001]
NMC93CS46(M8)@SOIC8 [DX1045]
NMC93CS46(MT8)@TSSOP8 [DX1059]
NMC93CS46(N) [DX0001]
NMC93CS56(M8)@SOIC8 [DX1045]
NMC93CS56(MT8)@TSSOP8 [DX1059]
NMC93CS56(N) [DX0001]
NMC93CS66(M8)@SOIC8 [DX1045]
NMC93CS66(MT8)@TSSOP8 [DX1059]
NMC93CS66(N) [DX0001]
NMC9817 [DX0001]

MICROCONTROLLER

ACE1001(M8)@SOIC8 [DX1045]
ACE1001(M8X)@SOIC8 [DX1045]
ACE1001(MT8)@TSSOP8 [DX1000]
ACE1001(MT8X)@TSSOP8 [DX1000]
ACE1001E(M8)@SOIC8 [DX1045]
ACE1001E(M8X)@SOIC8 [DX1045]
ACE1001E(MT8)@TSSOP8 [DX1000]
ACE1001E(MT8X)@TSSOP8 [DX1000]
ACE1001L(M8)@SOIC8 [DX1045]
ACE1001L(M8X)@SOIC8 [DX1045]
ACE1001L(MT8)@TSSOP8 [DX1000]
ACE1001L(MT8X)@TSSOP8 [DX1000]
ACE1101(EMT8)@TSSOP8 [DX1000]
ACE1101(EMT8X)@TSSOP8 [DX1000]
ACE1101(EN) [DX0001]
ACE1101(EN14) [DX0001]
ACE1101(LMT8)@TSSOP8 [DX1000]
ACE1101(LMT8X)@TSSOP8 [DX1000]
ACE1101(LN) [DX0001]
ACE1101(LN14) [DX0001]
ACE1101(MT8)@TSSOP8 [DX1000]
ACE1101(MT8X)@TSSOP8 [DX1000]

ACE1101(N) [DX0001]
ACE1101(N14) [DX0001]
ACE1101(VMT8)@TSSOP8 [DX1000]
ACE1101(VMT8X)@TSSOP8 [DX1000]
ACE1101(VN) [DX0001]
ACE1101(VN14) [DX0001]
ACE1101B(EMT8)@TSSOP8 [DX1000]
ACE1101B(EMT8X)@TSSOP8 [DX1000]
ACE1101B(EN) [DX0001]
ACE1101B(EN14) [DX0001]
ACE1101B(MT8)@TSSOP8 [DX1000]
ACE1101B(MT8X)@TSSOP8 [DX1000]
ACE1101B(N) [DX0001]
ACE1101B(N14) [DX0001]
ACE1101B(VMT8)@TSSOP8 [DX1000]
ACE1101B(VMT8X)@TSSOP8 [DX1000]
ACE1101B(VN) [DX0001]
ACE1101B(VN14) [DX0001]
ACE1202(dip14) [DX0001]
ACE1202(dip8) [DX0001]
ACE1202(M14)@SOIC14 [DX1016]
ACE1202(M8)@SOIC8 [DX1045]
ACE12022(dip14) [DX0001]
ACE12022(dip8) [DX0001]
ACE12022(M14)@SOIC14 [DX1016]
ACE12022(M8)@SOIC8 [DX1045]
ACE12022B(dip14) [DX0001]
ACE12022B(dip8) [DX0001]
ACE12022B(M14)@SOIC14 [DX1016]
ACE12022B(M8)@SOIC8 [DX1045]
ACE12022BE(dip14) [DX0001]
ACE12022BE(dip8) [DX0001]
ACE12022BE(M14)@SOIC14 [DX1016]
ACE12022BE(M8)@SOIC8 [DX1045]
ACE12022BV(dip14) [DX0001]
ACE12022BV(dip8) [DX0001]
ACE12022BV(M14)@SOIC14 [DX1016]
ACE12022BV(M8)@SOIC8 [DX1045]
ACE12022E(dip14) [DX0001]
ACE12022E(dip8) [DX0001]
ACE12022E(M14)@SOIC14 [DX1016]
ACE12022E(M8)@SOIC8 [DX1045]
ACE1202B(dip14) [DX0001]
ACE1202B(dip8) [DX0001]
ACE1202B(M14)@SOIC14 [DX1016]
ACE1202B(M8)@SOIC8 [DX1045]
ACE1202BE(dip14) [DX0001]
ACE1202BE(dip8) [DX0001]
ACE1202BE(M14)@SOIC14 [DX1016]
ACE1202BE(M8)@SOIC8 [DX1045]
ACE1202BV(dip14) [DX0001]
ACE1202BV(dip8) [DX0001]
ACE1202BV(M14)@SOIC14 [DX1016]
ACE1202BV(M8)@SOIC8 [DX1045]
ACE1202E(dip14) [DX0001]
ACE1202E(dip8) [DX0001]
ACE1202E(M14)@SOIC14 [DX1016]
ACE1202E(M8)@SOIC8 [DX1045]
ACE1202L(dip14) [DX0001]
ACE1202L(dip8) [DX0001]
ACE1202L(M14)@SOIC14 [DX1016]
ACE1202L(M8)@SOIC8 [DX1045]
ACE1202V(dip8)
ACE1202V(M14)@SOIC14 [DX1016]
ACE1202V(M8)@SOIC8 [DX1045]
ACE1501(EM)@SOIC14 [DX1016]
ACE1501(EM8)@SOIC8 [DX1045]
ACE1501(EM8X)@SOIC8 [DX1045]
ACE1501(EMT)@TSOP14 [DX1000]
ACE1501(EMT8)@TSSOP8 [DX1000]
ACE1501(EMT8X)@TSSOP8 [DX1000]
ACE1501(EMTX)@TSOP14 [DX1000]
ACE1501(EMX)@SOIC14 [DX1016]
ACE1501(EN) [DX0001]
ACE1501(EN14) [DX0001]
ACE1501(VM)@SOIC14 [DX1016]
ACE1501(VM8)@SOIC8 [DX1045]
ACE1501(VM8X)@SOIC8 [DX1045]
ACE1501(VMT)@TSOP14 [DX1000]
ACE1501(VMT8)@TSSOP8 [DX1000]
ACE1501(VMT8X)@TSSOP8 [DX1000]
ACE1501(VMTX)@TSOP14 [DX1000]
ACE1501(VMX)@SOIC14 [DX1016]
ACE1501(VN) [DX0001]
ACE1501(VN14) [DX0001]
ACE1502(EM)@SOIC14 [DX1016]
ACE1502(EM8)@SOIC8 [DX1045]
ACE1502(EMT)@TSOP14 [DX1000]
ACE1502(EMT8)@TSSOP8 [DX1000]
ACE1502(EN) [DX0001]
ACE1502(EN14) [DX0001]
ACE1502(VM)@SOIC14 [DX1016]
ACE1502(VM8)@SOIC8 [DX1045]
ACE1502(VMT)@TSOP14 [DX1000]
ACE1502(VMT8)@TSSOP8 [DX1000]
ACE1502(VN) [DX0001]

ACE1502(VN14) [DX0001]
ACE8000(M8X)@SOIC8 [DX1045]
ACE8000E(M8X)@SOIC8 [DX1045]
ACE8001(M8X)@SOIC8 [DX1045]
ACE8001(MT8X)@TSSOP8 [DX1000]
ACE8001E(M8X)@SOIC8 [DX1045]
ACE8001E(MT8X)@TSSOP8 [DX1000]
FMS7401L(EMT8X)@TSSOP8 [DX1000]
FMS7401L(EMX)@SOIC14 [DX1045]
FMS7401L(EN14) [DX0001]
FMS7401L(VN14) [DX0001]
ACE8000(M8)@SOIC8 [DX1045]
ACE8000E(M8)@SOIC8 [DX1045]
ACE8001(M8)@SOIC8 [DX1045]
ACE8001(MT8)@TSSOP8 [DX1000]
ACE8001E(M8)@SOIC8 [DX1045]
ACE8001E(MT8)@TSSOP8 [DX1000]
FMS7401L(EM8X)@SOIC8 [DX1045]
FMS7401L(EMTX)@TSSOP14 [DX1000]
FMS7401L(EN) [DX0001]
FMS7401L(VN) [DX0001]

FDI

E(E)PROM/FRAM/NVRAM

MSP55LV100G(low)@FBGA96 [DX5028]
MSP55LV100G(normal)@FBGA96 [DX5028]
MSP55LV100G@FBGA96 [DX5028]
MSP55LV128(fast)@PSOP44 [DX1014]
MSP55LV128T(*8)@TSOP56 [DX1011]
MSP55LV128T(fast)@PSOP44 [DX1014]
MSP55LV128T@PSOP44 [DX1014]
MSP55LV160@PSOP44 [DX1014]
MSP55LV256(fast)@PSOP44 [DX1014]
MSP55LV512@SSOP70 [DX1057]
MSP55LV650@PSOP44 [DX1014]
MSP55LV100GS@FBGA96 [DX5005]
MSP55LV128@PSOP44 [DX1014]
MSP55LV128T@TSOP56 [DX1011]
MSP55LV160A@PSOP44 [DX1014]
MSP55LV256@PSOP44 [DX1014]
MSP55LV512@SSOP70(new) [DX1057]

FIDELIX

E(E)PROM/FRAM/NVRAM

FM25M04A [DX0001#1]
FM25M04A-T08 [DX1044#1]
FM25M04A-V08 [DX1044#1]
FM25M08A [DX0001#1]
FM25M08A-S08 [DX1045#1]
FM25M08A-T08 [DX1044#1]
FM25M08A-W08 [DX4005#1]
FM25M16A-B24 [DX5146]
FM25M16A-S16 [DX1072#1]
FM25M16A-V08 [DX1059#3]
FM25M32A [DX0001#1]
FM25M32A-S08 [DX1045#1]
FM25M32A-T08 [DX1044#1]
FM25M32A-W08 [DX4005#1]
FM25M04A-S08 [DX1045#1]
FM25M04A-U08 [DX4002#1]
FM25M04A-W08 [DX4005#1]
FM25M08A-B24 [DX5146]
FM25M08A-S16 [DX1072#1]
FM25M08A-V08 [DX1044#1]
FM25M16A [DX0001#1]
FM25M16A-S08 [DX1045#1]
FM25M16A-T08 [DX1044#1]
FM25M16A-W08 [DX4005#1]
FM25M32A-B24 [DX5146]
FM25M32A-S16 [DX1072#1]
FM25M32A-V08 [DX1045#1]
FM25M4AA@SON8 [DX4005#1]

FM25M4AA@SOP16 [DX1033#1]
FM25M4AA@SOP8 [DX1044#1]
FM25M4AA@VSOP8 [DX1044#1]
FM25M4AA@WSON8
FM25M64A [DX0001#1]
FM25M64A-B24 [DX5146]
FM25M64A-S08 [DX1045#1]
FM25M64A-S16 [DX1072#1]
FM25M64A-T08 [DX1044#1]
FM25M64A-V08 [DX1045#1]
FM25M64A-W08 [DX4005#1]
FM25M64C [DX0001#1]
FM25M64C-B24 [DX5146]
FM25M64C-S08 [DX1045#1]
FM25M64C-S16 [DX1072#1]
FM25M64C-T08 [DX1044#1]
FM25M64C-V08 [DX1045#1]
FM25M64C-W08 [DX4005#1]
FM25Q08A [DX0001#1]
FM25Q08A-B24 [DX5146]
FM25Q08A-S08 [DX1045#1]
FM25Q08A-S16 [DX1072#1]
FM25Q08A-T08 [DX1044#1]
FM25Q08A-V08 [DX1059#3]
FM25Q08A-W08 [DX4005#1]
FM25Q16 [DX0001#1]
FM25Q16@SOP8 [DX1044#1]
FM25Q16@WSON8 [DX4005#1]
FM25Q16A [DX0001#1]
FM25Q16A@SOP8 [DX1045#1]
FM25Q16A@WSON8 [DX4005#1]
FM25Q16A-B24 [DX5146]
FM25Q16A-S16 [DX1072#1]
FM25Q16A-T08 [DX1044#1]
FM25Q16A-V08 [DX1059#3]
FM25Q16B [DX0001#1]
FM25Q16B-B24 [DX5146]
FM25Q16B-S08 [DX1045#1]
FM25Q16B-S16 [DX1072#1]
FM25Q16B-T08 [DX1044#1]
FM25Q16B-V08 [DX1059#3]
FM25Q16B-W08 [DX4005#1]
FM25Q32A [DX0001#1]
FM25Q32A@SOP16 [DX1072#1]
FM25Q32A@SOP8(150 mil) [DX1045#1]
FM25Q32A@SOP8(200 mil) [DX1044#1]
FM25Q32A@WSON8 [DX4005#1]
FM25Q32A-B24 [DX5146]
FM25Q32A-V08 [DX1045#1]
FM25Q64A [DX0001#1]
FM25Q64A-B24 [DX5146]
FM25Q64A-S08 [DX1045#1]
FM25Q64A-S16 [DX1072#1]
FM25Q64A-T08 [DX1044#1]
FM25Q64A-V08 [DX1045#1]
FM25Q64A-W08 [DX4005#1]
FM25S16A [DX0001#1]
FM25S16A-B24 [DX5146]
FM25S16A-S08 [DX1045#1]
FM25S16A-S16 [DX1072#1]
FM25S16A-T08 [DX1044#1]
FM25S16A-V08 [DX1059#3]
FM25S16A-W08 [DX4005#1]
FMN1ED5TBA@BGA137 [DX5011-1]
FMN1ED6SBA@BGA107 [DX5028]
FMN1ED6SBS@BGA107 [DX5028]
FMN1ES5TBA@BGA137 [DX5011-1]
FMN1ES6TBA@BGA137 [DX5011-1]
FMN1SD5SBA@BGA130 [DX5140-1]
FMN1SD5TBS@BGA130 [DX5140-1]
FMN1SD5TBS-50IB@BGA137 [DX5011-1]
FMN1SD6SBA@BGA130 [DX5140-1]
FMN1SD6SBS@BGA130 [DX5140-1]
FMN2ED1TBK@BGA130 [DX5140-1]
FMN2ED1TBK@BGA137 [DX5011-1]
FMND1G08S3B@BGA48 [DX5246-1]
FMND1G08U3B@BGA63 [DX5046-1]
FMND1G08U3B@TSOP48 [DX1004-3]

FIRST-RANK Technology

E(E)PROM/FRAM/NVRAM

T24C02 [DX0001]
T24C02@SOP8 [DX1045]

T24C02@TSSOP8 [DX1059]
T24C04 [DX0001]
T24C04@SOP8 [DX1045]
T24C04@TSSOP8 [DX1059]
T24C08 [DX0001]
T24C08@SOP8 [DX1045]
T24C08@TSSOP8 [DX1059]
T24C16 [DX0001]
T24C16@SOP8 [DX1045]
T24C16@TSSOP8 [DX1059]

FLEXTRONICS

MICROCONTROLLER

LPC2368@BGA100(new) [DX5055]

FOCALTECH

MICROCONTROLLER

FT5206GE1@QFN40 [DX4039]
FT5306DE4@QFN48 [DX4043]
FT5336GQQ@QFN48 [DX4093]
FT5406DQ9@QFN56 [DX4087]
FT5406EE8@QFN68 [DX4071]
FT6206GMA@QFN40 [DX4039]
FT6206GMA@QFN40(Left down) [DX4039]
FT6306DMB@QFN48 [DX4043]
FT6306DMB@QFN48(Left down) [DX4043]

FORCE TECHNOLOGIES

E(E)PROM/FRAM/NVRAM

FT24C01 [DX0001]
FT24C01@SOIC8 [DX1045]
FT24C01@TSOP8 [DX1059]
FT24C01A [DX0001]
FT24C01A@SOIC8 [DX1045]
FT24C01A@TSOP8 [DX1059]
FT24C02 [DX0001]
FT24C02@SOIC8 [DX1045]
FT24C02@TSOP8 [DX1059]
FT24C02A [DX0001]
FT24C02A@SOIC8 [DX1045]
FT24C02A@TSOP8 [DX1059]
FT24C04 [DX0001]
FT24C04@SOIC8 [DX1045]
FT24C04@TSOP8 [DX1059]
FT24C04A [DX0001]
FT24C04A@SOIC8 [DX1045]
FT24C04A@TSOP8 [DX1059]
FT24C08 [DX0001]
FT24C08@SOIC8 [DX1045]
FT24C08@TSOP8 [DX1059]
FT24C08A [DX0001]
FT24C08A@SOIC8 [DX1045]
FT24C08A@TSOP8 [DX1059]
FT24C128 [DX0001]
FT24C128@SOIC8 [DX1045]
FT24C128@TSOP8 [DX1059]
FT24C128A [DX0001]
FT24C128A@SOIC8 [DX1045]
FT24C128A@TSOP8 [DX1059]
FT24C16 [DX0001]
FT24C16@SOIC8 [DX1045]
FT24C16@TSOP8 [DX1059]
FT24C16A [DX0001]
FT24C16A@SOIC8 [DX1045]
FT24C16A@TSOP8 [DX1059]

FT24C256 [DX0001]
FT24C256@TSOP8 [DX1059]
FT24C256A@SOIC8 [DX1045]
FT24C32 [DX0001]
FT24C32@TSOP8 [DX1059]
FT24C32A@SOIC8 [DX1045]
FT24C64 [DX0001]
FT24C64@TSOP8 [DX1059]
FT24C64A@SOIC8 [DX1045]
FT27C010 [DX0001]
FT27C010@TSOP32 [DX1002]
FT27C020@PLCC32 [DX2032]
FT27C040 [DX0001]
FT27C040@TSOP32 [DX1002]
FT27C256 [DX0001]
FT27C64 [DX0001]
FT27HC256 [DX0001]
FT27HC64 [DX0001]
FT28C010 [DX0001]
FT28C010@PLCC32 [DX2032]
FT28C010@TSOP32 [DX1002]
FT28C010E@JLCC32 [DX2132]
FT28C010E@PLCC44 [DX2044]
FT28C020 [DX0001]
FT28C020@PLCC32 [DX2032]
FT28C020@TSOP32 [DX1002]
FT28C040@JLCC32 [DX2132]
FT28C040@PLCC44 [DX2044]
FT28C16 [DX0001]
FT28C256 [DX0001]
FT28C256@PLCC32 [DX2032]
FT28C256@TSOP28 [DX1024]
FT28C256B@JLCC32 [DX2132]
FT28C256B@SOIC28 [DX1033]
FT28C64 [DX0001]
FT28C64@SOIC28 [DX1033]
FT28C64B [DX0001]
FT28C64B@PLCC32 [DX2032]
FT28C64B@TSOP28 [DX1024]
FT28C64X@PLCC32 [DX2032]
FT28C64X@TSOP28 [DX1024]
FT28HC64@PLCC32 [DX2032]
FT58C1001 [DX0001]
FT58C1001@VSOP32 [DX1003]
FT24C256@SOIC8 [DX1045]
FT24C256A [DX0001]
FT24C256A@TSOP8 [DX1059]
FT24C32@SOIC8 [DX1045]
FT24C32A [DX0001]
FT24C32A@TSOP8 [DX1059]
FT24C64@SOIC8 [DX1045]
FT24C64A [DX0001]
FT24C64A@TSOP8 [DX1059]
FT27C010@PLCC32 [DX2032]
FT27C020 [DX0001]
FT27C020@TSOP32
FT27C040@PLCC32 [DX2032]
FT27C16 [DX0001]
FT27C256@PLCC32 [DX2032]
FT27C64@PLCC32 [DX2032]
FT27HC256@PLCC32 [DX2032]
FT27HC64@PLCC32 [DX2032]
FT28C010@JLCC32 [DX2132]
FT28C010@PLCC44 [DX2044]
FT28C010E [DX0001]
FT28C010E@PLCC32 [DX2032]
FT28C010E@TSOP32 [DX1002]
FT28C020@JLCC32 [DX2132]
FT28C020@PLCC44 [DX2044]
FT28C040 [DX0001]
FT28C040@PLCC32 [DX2032]
FT28C040@TSOP32 [DX1002]
FT28C16@PLCC32 [DX2032]
FT28C256@JLCC32 [DX2132]
FT28C256@SOIC28 [DX1033]
FT28C256B [DX0001]
FT28C256B@PLCC32 [DX2032]
FT28C256B@TSOP28 [DX1024]
FT28C64@PLCC32 [DX2032]
FT28C64@TSOP28 [DX1024]
FT28C64B@JLCC32 [DX2132]
FT28C64B@SOIC28 [DX1033]
FT28C64X [DX0001]
FT28C64X@SOIC28 [DX1033]
FT28HC64 [DX0001]
FT28HC64@TSOP28 [DX1024]
FT58C1001@SSOP32 [DX1020]

FORCREAT

MICROCONTROLLER

uPD78F0524AGB@QFP52 [DX3010]
uPD78F0524GB@QFP52 [DX3010]

FORWARD

E(E)PROM/FRAM/NVRAM

24LC01 [DX0001]
24LC02 [DX0001]
24LC04 [DX0001]
24LC08 [DX0001]
24LC16 [DX0001]
24LC32 [DX0001]
24LC64 [DX0001]
24LC01@SOIC8 [DX1045]
24LC02@SOIC8 [DX1045]
24LC04@SOIC8 [DX1045]
24LC08@SOIC8 [DX1045]
24LC16@SOIC8 [DX1045]
24LC32@SOIC8 [DX1045]
24LC64@SOIC8 [DX1045]

FREESCALE

E(E)PROM/FRAM/NVRAM

MR2A16A@TSOP44 [DX1046]

MICROCONTROLLER

DSP56F801(FA60)@TQFP48 [DX3007]
DSP56F801(FA80)@TQFP48 [DX3007]
DSP56F802(TA60)@TQFP32 [DX3001]
DSP56F802(TA80)@TQFP32 [DX3001]
DSP56F803(BU80)@TQFP100 [DX3021]
DSP56F803(BU80E)@TQFP100 [DX3021]
DSP56F805(FV80)@TQFP144 [DX3035]
DSP56F805(FV80E)@TQFP144 [DX3035]
DSP56F807(PY80)@LQFP160 [DX3090]
DSP56F807(PY80E)@LQFP160 [DX3090]
DSP56F807(PY80E)@LQFP160(ISP)
DSP56F807(VF80E)@LQFP160(ISP)
DSP56F826(BU80)@TQFP100(ISP)
DSP56F826(BU80E)@TQFP100 [DX3021]
DSP56F826(BU80E)@TQFP100(ISP)
DSP56F827(FG80E)@TQFP128 [DX3032]
MC13211@QFN65 [DX4023]
MC13213@QFN65 [DX4023]
MC56F8002VWL@SOIC28 [DX1033]
MC56F8006VLF@QFP48 [DX3007]
MC56F8011VFAE@QFP32 [DX3001]
MC56F8014VFAE@QFP32 [DX3001]
DSP56F801(FA60E)@TQFP48 [DX3007]
DSP56F801(FA80E)@TQFP48 [DX3007]
DSP56F802(TA60E)@TQFP32 [DX3001]
DSP56F802(TA80E)@TQFP32 [DX3001]
DSP56F807(PY80)@LQFP160(ISP)
DSP56F807(VF80)@LQFP160(ISP)
DSP56F826(BU80)@TQFP100 [DX3021]
DSP56F827(FG80)@TQFP128 [DX3032]
MC13212@QFN65 [DX4023]
MC13214@QFN65 [DX4023]
MC56F8006VLC@QFP32 [DX3001]
MC56F8006VWL@SOIC28 [DX1033]
MC56F8013VFAE@QFP32 [DX3001]
MC56F8023MFAE@QFP32 [DX3001]

MC56F8023VFAE@QFP32 [DX3001]
MC56F8025VLD@QFP44 [DX3003]
MC56F8027VLD@QFP64 [DX3011]
MC56F8033VLC@QFP32 [DX3001]
MC56F8035VLD@QFP44 [DX3003]
MC56F8036MFAE@QFP48 [DX3007]
MC56F8036VFAE@QFP48 [DX3007]
MC56F8037VLH@QFP64 [DX3011]
MC56F8122MFA@QFP48 [DX3007]
MC56F8122MFAE@QFP48 [DX3007]
MC56F8122VFA@QFP48 [DX3007]
MC56F8122VFAE@QFP48 [DX3007]
MC56F8123MFB@QFP64 [DX3011]
MC56F8123MFBE@QFP64 [DX3011]
MC56F8123VFB@QFP64 [DX3011]
MC56F8123VFBE@QFP64 [DX3011]
MC56F8135MFG@PQFP128 [DX3032]
MC56F8135MFGE@PQFP128 [DX3032]
MC56F8135VFG@PQFP128 [DX3032]
MC56F8135VFGE@PQFP128 [DX3032]
MC56F8145MFG@PQFP128 [DX3032]
MC56F8145MFGE@PQFP128 [DX3032]
MC56F8145VFG@PQFP128 [DX3032]
MC56F8145VFGE@PQFP128 [DX3032]
MC56F8146MFV@QFP144 [DX3035]
MC56F8146MFVE@QFP144 [DX3035]
MC56F8146VFV@QFP144 [DX3035]
MC56F8146VFVE@QFP144 [DX3035]
MC56F8147MPY@QFP160 [TA083A-B084]
MC56F8147MPYE@QFP160 [TA083A-B084]
MC56F8147VPY@QFP160 [TA083A-B084]
MC56F8147VPYE@QFP160 [TA083A-B084]
MC56F8155MFG@PQFP128 [DX3032]
MC56F8155MFGE@PQFP128 [DX3032]
MC56F8155VFG@PQFP128 [DX3032]
MC56F8155VFGE@PQFP128 [DX3032]
MC56F8156MFV@QFP144 [DX3035]
MC56F8156MFVE@QFP144 [DX3035]
MC56F8156VFV@QFP144 [DX3035]
MC56F8156VFVE@QFP144 [DX3035]
MC56F8157MPY@QFP160 [TA083A-B084]
MC56F8157MPYE@QFP160 [TA083A-B084]
MC56F8157VPY@QFP160 [TA083A-B084]
MC56F8157VPYE@QFP160 [TA083A-B084]
MC56F8165MFG@PQFP128 [DX3032]
MC56F8165MFGE@PQFP128 [DX3032]
MC56F8165VFG@PQFP128 [DX3032]
MC56F8165VFGE@PQFP128 [DX3032]
MC56F8166MFV@QFP144 [DX3035]
MC56F8166MFVE@QFP144 [DX3035]
MC56F8166VFV@QFP144 [DX3035]
MC56F8166VFVE@QFP144 [DX3035]
MC56F8167MPY@QFP160 [TA083A-B084]
MC56F8167MPYE@QFP160 [TA083A-B084]
MC56F8167VPY@QFP160 [TA083A-B084]
MC56F8167VPYE@QFP160 [TA083A-B084]
MC56F8246MLF@QFP48 [DX3007]
MC56F8246VLF@QFP48 [DX3007]
MC56F8247MLH@QFP64 [DX3011]
MC56F8247VLH@QFP64 [DX3011]
MC56F8256MLF@QFP48 [DX3007]
MC56F8256VLF@QFP48 [DX3007]
MC56F8257MLH@QFP64 [DX3011]
MC56F8257VLH@QFP64 [DX3011]
MC56F8322MFA@QFP48 [DX3007]
MC56F8322MFAE@QFP48 [DX3007]
MC56F8322VFA@QFP48 [DX3007]
MC56F8322VFAE@QFP48 [DX3007]
MC56F8323MFB@QFP64 [DX3011]
MC56F8323MFBE@QFP64 [DX3011]
MC56F8323VFB@QFP64 [DX3011]
MC56F8323VFBE@QFP64 [DX3011]
MC56F8335MFG@PQFP128 [DX3032]
MC56F8335MFGE@PQFP128 [DX3032]
MC56F8335VFG@PQFP128 [DX3032]
MC56F8335VFGE@PQFP128 [DX3032]
MC56F8345MFG@PQFP128 [DX3032]
MC56F8345MFGE@PQFP128 [DX3032]
MC56F8345VFG@PQFP128 [DX3032]
MC56F8345VFGE@PQFP128 [DX3032]
MC56F8346MFV@QFP144 [DX3035]
MC56F8346MFVE@QFP144 [DX3035]
MC56F8346VFV@QFP144 [DX3035]
MC56F8346VFVE@QFP144 [DX3035]

MC56F8347MPY@QFP160 [TA083A-B084]
MC56F8347MPYE@QFP160 [TA083A-B084]
MC56F8347VPY@QFP160 [TA083A-B084]
MC56F8347VPYE@QFP160 [TA083A-B084]
MC56F8355MFG@PQFP128 [DX3032]
MC56F8355MFGE@PQFP128 [DX3032]
MC56F8355VFG@PQFP128 [DX3032]
MC56F8355VFGE@PQFP128 [DX3032]
MC56F8356MFV@QFP144 [DX3035]
MC56F8356MFVE@QFP144 [DX3035]
MC56F8356VFV@QFP144 [DX3035]
MC56F8356VFVE@QFP144 [DX3035]
MC56F8357MPY@QFP160 [TA083A-B084]
MC56F8357MPYE@QFP160 [TA083A-B084]
MC56F8357VPY@QFP160 [TA083A-B084]
MC56F8357VPYE@QFP160 [TA083A-B084]
MC56F8365MFG@PQFP128 [DX3032]
MC56F8365MFGE@PQFP128 [DX3032]
MC56F8365VFG@PQFP128 [DX3032]
MC56F8365VFGE@PQFP128 [DX3032]
MC56F8366MFV@QFP144 [DX3035]
MC56F8366MFVE@QFP144 [DX3035]
MC56F8366VFV@QFP144 [DX3035]
MC56F8366VFVE@QFP144 [DX3035]
MC56F8367MPY@QFP160 [TA083A-B084]
MC56F8367MPYE@QFP160 [TA083A-B084]
MC56F8367VPY@QFP160 [TA083A-B084]
MC56F8367VPYE@QFP160 [TA083A-B084]
MC56F84452VLH@TQFP64 [DX3011]
MC68HC11A0 [DX0001]
MC68HC11A0@PLCC52 [DX2052]
MC68HC11A1 [DX0001]
MC68HC11A1@PLCC52 [DX2052]
MC68HC11A8 [DX0001]
MC68HC11A8@PLCC52 [DX2052]
MC68HC11E1@PLCC52 [DX2052]
MC68HC11E1@QFP52 [DX3010]
MC68HC11E1CFN2 [DX2052]
MC68HC11E1CFN3 [DX2052]
MC68HC11E1CFU2 [DX3044]
MC68HC11E1CFU3 [DX3044]
MC68HC11E1MFN2 [DX2052]
MC68HC11E1MFU2 [DX3044]
MC68HC11E1VFN2 [DX2052]
MC68HC11E1VFU2 [DX3044]
MC68HC11E20@PLCC52 [DX2052]
MC68HC11E20@QFP52 [DX3010]
MC68HC11E20CFN2 [DX2052]
MC68HC11E20CFN3 [DX2052]
MC68HC11E20CFU2 [DX3044]
MC68HC11E20CFU3 [DX3044]
MC68HC11E20MFN2 [DX2052]
MC68HC11E20MFU2 [DX3044]
MC68HC11E20VFN2 [DX2052]
MC68HC11E20VFU2 [DX3044]
MC68HC11E9@PLCC52 [DX2052]
MC68HC11E9@QFP52 [DX3010]
MC68HC11E9CFN2 [DX2052]
MC68HC11E9CFN3 [DX2052]
MC68HC11E9CFU2 [DX3044]
MC68HC11E9CFU3 [DX3044]
MC68HC11E9MFN2 [DX2052]
MC68HC11E9MFU2 [DX3044]
MC68HC11E9VFN2 [DX2052]
MC68HC11E9VFU2 [DX3044]
MC68HC11EA9CFN2 [DX2052]
MC68HC11EA9CFN3 [DX2052]
MC68HC11EA9CFS2 [DX2052]
MC68HC11EA9CFS3 [DX2052]
MC68HC11EA9MFN2 [DX2052]
MC68HC11EA9MFN3 [DX2052]
MC68HC11EA9MFS2 [DX2052]
MC68HC11EA9MFS3 [DX2052]
MC68HC11EA9VFN2 [DX2052]
MC68HC11EA9VFN3 [DX2052]
MC68HC11EA9VFS2 [DX2052]
MC68HC11EA9VFS3 [DX2052]
MC68HC11F1@PLCC68 [DX2068]
MC68HC11F1A@PLCC68 [DX2068]
MC68HC11F1ACFN2 [DX2068]
MC68HC11F1ACFN3 [DX2068]
MC68HC11F1ACFN4 [DX2068]
MC68HC11F1ACPU2 [DX3017]
MC68HC11F1ACPU3 [DX3017]

MC68HC11F1ACPU4 [DX3017]
MC68HC11F1AMFN2 [DX2068]
MC68HC11F1AMFN3 [DX2068]
MC68HC11F1AMFN4 [DX2068]
MC68HC11F1AMPU2 [DX3017]
MC68HC11F1AMPU3 [DX3017]
MC68HC11F1AMPU4 [DX3017]
MC68HC11F1AVFN2 [DX2068]
MC68HC11F1AVFN3 [DX2068]
MC68HC11F1AVFN4 [DX2068]
MC68HC11F1AVPU2 [DX3017]
MC68HC11F1AVPU3 [DX3017]
MC68HC11F1AVPU4 [DX3017]
MC68HC11F1CFN2 [DX2068]
MC68HC11F1CFN3 [DX2068]
MC68HC11F1CFN4 [DX2068]
MC68HC11F1CPU2 [DX3017]
MC68HC11F1CPU3 [DX3017]
MC68HC11F1CPU4 [DX3017]
MC68HC11F1MFN2 [DX2068]
MC68HC11F1MFN3 [DX2068]
MC68HC11F1MFN4 [DX2068]
MC68HC11F1MPU2 [DX3017]
MC68HC11F1MPU3 [DX3017]
MC68HC11F1MPU4 [DX3017]
MC68HC11F1VFN2 [DX2068]
MC68HC11F1VFN3 [DX2068]
MC68HC11F1VFN4 [DX2068]
MC68HC11F1VPU2 [DX3017]
MC68HC11F1VPU3 [DX3017]
MC68HC11F1VPU4 [DX3017]
MC68HC11K1@PLCC84 [DX2084]
MC68HC11K1@TQFP80 [DX3018]
MC68HC11KS2@PLCC68 [DX2068]
MC68HC11P1CFN3 [DX2084]
MC68HC11P1CFN4 [DX2084]
MC68HC11P2CFN3 [DX2084]
MC68HC11P2CFN4 [DX2084]
MC68HC11P3CFN3 [DX2084]
MC68HC11P3CFN4 [DX2084]
MC68HC705B16B [DX0056]
MC68HC705B16CB [DX0056]
MC68HC705B16CFN [DX2052]
MC68HC705B16CFU [DX3013]
MC68HC705B16FN [DX2052]
MC68HC705B16FU [DX3013]
MC68HC705B16NB [DX0056]
MC68HC705B16NCB [DX0056]
MC68HC705B16NCFN [DX2052]
MC68HC705B16NCFU [DX3013]
MC68HC705B16NFN [DX2052]
MC68HC705B16NFU [DX3013]
MC68HC705C4 [DX0001]
MC68HC705C4@PLCC44 [DX2044]
MC68HC705C4A [DX0001]
MC68HC705C4A@PLCC44 [DX2044]
MC68HC705C8 [DX0001]
MC68HC705C8@PLCC44 [DX2044]
MC68HC705C8@SDIP42 [DX0042]
MC68HC705C8@TQFP44 [DX3002]
MC68HC705C8A [DX0001]
MC68HC705C8A@PLCC44 [DX2044]
MC68HC705C8A@SDIP42 [DX0042]
MC68HC705C8A@TQFP44 [DX3002]
MC68HC705C9A [DX0001]
MC68HC705C9A@PLCC44 [DX2044]
MC68HC705C9A@TQFP44 [DX3002]
MC68HC705J1ACDW [DX1033]
MC68HC705J1ACP [DX0001]
MC68HC705J1ACS [DX1001]
MC68HC705J1ADW [DX1033]
MC68HC705J1AP [DX0001]
MC68HC705J1AS [DX1001]
MC68HC705KJ1CDW [DX1033]
MC68HC705KJ1CP [DX0001]
MC68HC705KJ1CS [DX1001]
MC68HC705KJ1DW [DX1033]
MC68HC705KJ1P [DX0001]
MC68HC705KJ1S [DX1001]
MC68HC705P6(CDW)@SOIC28 [DX1033]
MC68HC705P6(CP) [DX0001]
MC68HC705P6A(CDW)@SOIC28 [DX1033]
MC68HC705P6A(CP) [DX0001]
MC68HC705P9 [DX0001]
MC68HC705P9@SOIC28 [DX1033]
MC68HC705SR3 [DX0001]
MC68HC705SR3@SDIP42 [DX0042]
MC68HC705SR3@TQFP44 [DX3005]
MC68HC711D3 [DX0001]
MC68HC711D3(3V) [DX0001]
MC68HC711D3(3V)@PLCC44 [DX2044]
MC68HC711D3(3V)@TQFP44 [DX3002]
MC68HC711D3@PLCC44 [DX2044]
MC68HC711D3@TQFP44 [DX3002]

MC68HC711E20@PLCC52 [DX2052]
MC68HC711E9@PLCC52 [DX2052]
MC68HC711E9CFN@PLCC52 [DX2052]
MC68HC711E9CFN2@PLCC52 [DX2052]
MC68HC711E9CFN3@PLCC52 [DX2052]
MC68HC711E9CFNE@PLCC52 [DX2052]
MC68HC711E9CFNE2@PLCC52 [DX2052]
MC68HC711E9CFNE3@PLCC52 [DX2052]
MC68HC711E9FN@PLCC52 [DX2052]
MC68HC711E9MFN2@PLCC52 [DX2052]
MC68HC711E9MFNE2@PLCC52 [DX2052]
MC68HC711E9VFN2@PLCC52 [DX2052]
MC68HC711E9VFNE2@PLCC52 [DX2052]
MC68HC711EA9CFN2 [DX2052]
MC68HC711EA9CFN3 [DX2052]
MC68HC711EA9CFS2 [DX2052]
MC68HC711EA9CFS3 [DX2052]
MC68HC711EA9MFN2 [DX2052]
MC68HC711EA9MFN3 [DX2052]
MC68HC711EA9MFS2 [DX2052]
MC68HC711EA9MFS3 [DX2052]
MC68HC711EA9VFN2 [DX2052]
MC68HC711EA9VFN3 [DX2052]
MC68HC711EA9VFS2 [DX2052]
MC68HC711EA9VFS3 [DX2052]
MC68HC711K4@PLCC84 [DX2084]
MC68HC711K4@TQFP80 [DX3018]
MC68HC711KA2@PLCC68 [DX2068]
MC68HC711KA3@PLCC68 [DX2068]
MC68HC711KA4@PLCC68 [DX2068]
MC68HC711KS2@PLCC68 [DX2068]
MC68HC711L6@PLCC68 [DX2068]
MC68HC711L6@TQFP64 [DX3013]
MC68HC711P2CFN3 [DX2084]
MC68HC711P2CFN4 [DX2084]
MC68HC711P2CFS3 [DX2084]
MC68HC711P2CFS4 [DX2084]
MC68HC811E2 [DX0001]
MC68HC811E2@PLCC52 [DX2052]
MC68HC811E2C [DX0001]
MC68HC811E2M [DX0001]
MC68HC811E2V [DX0001]
MC68HC812A4CPV@TQFP112 [DX3026]
MC68HC812A4CPVE@TQFP112 [DX3026]
MC68HC812A4MPV@TQFP112 [DX3026]
MC68HC812A4MPVE@TQFP112 [DX3026]
MC68HC812A4VPV@TQFP112 [DX3026]
MC68HC812A4VPVE@TQFP112 [DX3026]
MC68HC908AB32CFU@TQFP64 [DX3014]
MC68HC908AB32CFUE@TQFP64 [DX3014]
MC68HC908AB32MFU@TQFP64 [DX3014]
MC68HC908AB32MFUE@TQFP64 [DX3014]
MC68HC908AB32VFU@TQFP64 [DX3014]
MC68HC908AB32VFUE@TQFP64 [DX3014]
MC68HC908AP16CB@SDIP42 [DX0042]
MC68HC908AP16CBE@SDIP42 [DX0042]
MC68HC908AP16CFA@LQFP48 [DX3007]
MC68HC908AP16CFAE@LQFP48 [DX3007]
MC68HC908AP16CFB@TQFP44 [DX3002]
MC68HC908AP16CFBE@TQFP44 [DX3002]
MC68HC908AP16MB@SDIP42 [DX0042]
MC68HC908AP16MBE@SDIP42 [DX0042]
MC68HC908AP16MFA@LQFP48 [DX3007]
MC68HC908AP16MFAE@LQFP48 [DX3007]
MC68HC908AP16MFB@TQFP44 [DX3002]
MC68HC908AP16MFBE@TQFP44 [DX3002]
MC68HC908AP16VB@SDIP42 [DX0042]
MC68HC908AP16VBE@SDIP42 [DX0042]
MC68HC908AP16VFA@LQFP48 [DX3007]
MC68HC908AP16VFAE@LQFP48 [DX3007]
MC68HC908AP16VFB@TQFP44 [DX3002]
MC68HC908AP16VFBE@TQFP44 [DX3002]
MC68HC908AP32CB@SDIP42 [DX0042]
MC68HC908AP32CBE@SDIP42 [DX0042]
MC68HC908AP32CFA@LQFP48 [DX3007]
MC68HC908AP32CFAE@LQFP48 [DX3007]

MC68HC908AP32CFB@TQFP44 [DX3002]
MC68HC908AP32CFBE@TQFP44 [DX3002]
MC68HC908AP32MB@SDIP42 [DX0042]
MC68HC908AP32MBE@SDIP42 [DX0042]
MC68HC908AP32MFA@LQFP48 [DX3007]
MC68HC908AP32MFAE@LQFP48 [DX3007]
MC68HC908AP32MFB@TQFP44 [DX3002]
MC68HC908AP32MFBE@TQFP44 [DX3002]
MC68HC908AP32VB@SDIP42 [DX0042]
MC68HC908AP32VBE@SDIP42 [DX0042]
MC68HC908AP32VFA@LQFP48 [DX3007]
MC68HC908AP32VFAE@LQFP48 [DX3007]
MC68HC908AP32VFB@TQFP44 [DX3002]
MC68HC908AP32VFBE@TQFP44 [DX3002]
MC68HC908AP64CB@SDIP42 [DX0042]
MC68HC908AP64CBE@SDIP42 [DX0042]
MC68HC908AP64CFA@LQFP48 [DX3007]
MC68HC908AP64CFAE@LQFP48 [DX3007]
MC68HC908AP64CFB@TQFP44 [DX3002]
MC68HC908AP64CFBE@TQFP44 [DX3002]
MC68HC908AP64MB@SDIP42 [DX0042]
MC68HC908AP64MBE@SDIP42 [DX0042]
MC68HC908AP64MFA@LQFP48 [DX3007]
MC68HC908AP64MFAE@LQFP48 [DX3007]
MC68HC908AP64MFB@TQFP44 [DX3002]
MC68HC908AP64MFBE@TQFP44 [DX3002]
MC68HC908AP64VB@SDIP42 [DX0042]
MC68HC908AP64VBE@SDIP42 [DX0042]
MC68HC908AP64VFA@LQFP48 [DX3007]
MC68HC908AP64VFAE@LQFP48 [DX3007]
MC68HC908AP64VFB@TQFP44 [DX3002]
MC68HC908AP64VFBE@TQFP44 [DX3002]
MC68HC908AP8CB@SDIP42 [DX0042]
MC68HC908AP8CBE@SDIP42 [DX0042]
MC68HC908AP8CFA@LQFP48 [DX3007]
MC68HC908AP8CFAE@LQFP48 [DX3007]
MC68HC908AP8CFB@TQFP44 [DX3002]
MC68HC908AP8CFBE@TQFP44 [DX3002]
MC68HC908AP8MB@SDIP42 [DX0042]
MC68HC908AP8MBE@SDIP42 [DX0042]
MC68HC908AP8MFA@LQFP48 [DX3007]
MC68HC908AP8MFAE@LQFP48 [DX3007]
MC68HC908AP8MFB@TQFP44 [DX3002]
MC68HC908AP8MFBE@TQFP44 [DX3002]
MC68HC908AP8VB@SDIP42 [DX0042]
MC68HC908AP8VBE@SDIP42 [DX0042]
MC68HC908AP8VFA@LQFP48 [DX3007]
MC68HC908AP8VFAE@LQFP48 [DX3007]
MC68HC908AP8VFB@TQFP44 [DX3002]
MC68HC908AP8VFBE@TQFP44 [DX3002]
MC68HC908AS32ACFN@PLCC52 [DX2052]
MC68HC908AS32ACFNE@PLCC52 [DX2052]
MC68HC908AS32ACFU@TQFP64 [DX3014]
MC68HC908AS32ACFUE@TQFP64 [DX3014]
MC68HC908AS32AMFN@PLCC52 [DX2052]
MC68HC908AS32AMFNE@PLCC52 [DX2052]
MC68HC908AS32AMFU@TQFP64 [DX3014]
MC68HC908AS32AMFUE@TQFP64 [DX3014]
MC68HC908AS32AVFN@PLCC52 [DX2052]
MC68HC908AS32AVFNE@PLCC52 [DX2052]
MC68HC908AS32AVFU@TQFP64 [DX3014]
MC68HC908AS32AVFUE@TQFP64 [DX3014]

MC68HC908AS60ACFN@PLCC52 [DX2052]
MC68HC908AS60ACFU@TQFP64 [DX3014]
MC68HC908AS60AMFN@PLCC52 [DX2052]
MC68HC908AS60AMFU@TQFP64 [DX3014]
MC68HC908AS60AVFN@PLCC52 [DX2052]
MC68HC908AS60AVFU@TQFP64 [DX3014]
MC68HC908AS60CFN@PLCC52 [DX2052]
MC68HC908AS60CFU@TQFP64 [DX3014]
MC68HC908AS60MFN@PLCC52 [DX2052]
MC68HC908AS60MFU@TQFP64 [DX3014]
MC68HC908AS60VFN@PLCC52 [DX2052]
MC68HC908AS60VFU@TQFP64 [DX3014]
MC68HC908AZ32ACFU@TQFP64 [DX3014]
MC68HC908AZ32ACFUE@TQFP64 [DX3014]
MC68HC908AZ32AMFU@TQFP64 [DX3014]
MC68HC908AZ32AMFUE@TQFP64 [DX3014]
MC68HC908AZ32AVFU@TQFP64 [DX3014]
MC68HC908AZ32AVFUE@TQFP64 [DX3014]
MC68HC908AZ60ACFU@TQFP64 [DX3014]
MC68HC908AZ60ACFUE@TQFP64 [DX3014]
MC68HC908AZ60AMFU@TQFP64 [DX3014]
MC68HC908AZ60AMFUE@TQFP64 [DX3014]
MC68HC908AZ60AVFU@TQFP64 [DX3014]
MC68HC908AZ60AVFUE@TQFP64 [DX3014]
MC68HC908AZ60CFU@TQFP64 [DX3014]
MC68HC908AZ60MFU@TQFP64 [DX3014]
MC68HC908AZ60VFU@TQFP64 [DX3014]
MC68HC908BD48IB@SDIP42 [DX0042]
MC68HC908BD48IBE@SDIP42 [DX0042]
MC68HC908BD48IFB@TQFP44 [DX3002]
MC68HC908BD48IFBE@TQFP44 [DX3002]
MC68HC908EY16ACFJ@TQFP32 [DX3001]
MC68HC908EY16ACFJE@TQFP32 [DX3001]
MC68HC908EY16AKFJ@TQFP32 [DX3001]
MC68HC908EY16AKFJE@TQFP32 [DX3001]
MC68HC908EY16AMFJ@TQFP32 [DX3001]
MC68HC908EY16AMFJE@TQFP32 [DX3001]
MC68HC908EY16AVFJ@TQFP32 [DX3001]
MC68HC908EY16AVFJE@TQFP32 [DX3001]
MC68HC908EY16CFA@TQFP32 [DX3001]
MC68HC908EY16CFAE@TQFP32 [DX3001]
MC68HC908EY16KFA@TQFP32 [DX3001]
MC68HC908EY16KFAE@TQFP32 [DX3001]
MC68HC908EY16MFA@TQFP32 [DX3001]
MC68HC908EY16MFAE@TQFP32 [DX3001]
MC68HC908EY16VFA@TQFP32 [DX3001]
MC68HC908EY16VFAE@TQFP32 [DX3001]
MC68HC908EY8ACFJ@TQFP32 [DX3001]
MC68HC908EY8ACFJE@TQFP32 [DX3001]
MC68HC908EY8AKFJ@TQFP32 [DX3001]
MC68HC908EY8AKFJE@TQFP32 [DX3001]
MC68HC908EY8AMFJ@TQFP32 [DX3001]
MC68HC908EY8AMFJE@TQFP32 [DX3001]
MC68HC908EY8AVFJ@TQFP32 [DX3001]

MC68HC908EY8AVFJE@TQFP32 [DX3001]
MC68HC908EY8CFA@TQFP32 [DX3001]
MC68HC908EY8CFAE@TQFP32 [DX3001]
MC68HC908EY8KFA@TQFP32 [DX3001]
MC68HC908EY8KFAE@TQFP32 [DX3001]
MC68HC908EY8MFA@TQFP32 [DX3001]
MC68HC908EY8MFAE@TQFP32 [DX3001]
MC68HC908EY8VFA@TQFP32 [DX3001]
MC68HC908EY8VFAE@TQFP32 [DX3001]
MC68HC908GP32CB@SDIP42 [DX0042]
MC68HC908GP32CBE@SDIP42 [DX0042]
MC68HC908GP32CFB@TQFP44 [DX3002]
MC68HC908GP32CFBE@TQFP44 [DX3002]
MC68HC908GP32CP
MC68HC908GP32CPE
MC68HC908GP32MB@SDIP42 [DX0042]
MC68HC908GP32MBE@SDIP42 [DX0042]
MC68HC908GP32MFB@TQFP44 [DX3002]
MC68HC908GP32MFBE@TQFP44 [DX3002]
MC68HC908GP32MP
MC68HC908GP32MPE
MC68HC908GP32VB@SDIP42 [DX0042]
MC68HC908GP32VBE@SDIP42 [DX0042]
MC68HC908GP32VFB@TQFP44 [DX3002]
MC68HC908GP32VFBE@TQFP44 [DX3002]
MC68HC908GP32VP
MC68HC908GP32VPE
MC68HC908GR16ACFA@TQFP48 [DX3007]
MC68HC908GR16ACFAE@TQFP48 [DX3007]
MC68HC908GR16ACFJ@TQFP32 [DX3001]
MC68HC908GR16ACFJE@TQFP32 [DX3001]
MC68HC908GR16AMFA@TQFP48 [DX3007]
MC68HC908GR16AMFAE@TQFP48 [DX3007]
MC68HC908GR16AMFJ@TQFP32 [DX3001]
MC68HC908GR16AMFJE@TQFP32 [DX3001]
MC68HC908GR16AVFA@TQFP48 [DX3007]
MC68HC908GR16AVFAE@TQFP48 [DX3007]
MC68HC908GR16AVFJ@TQFP32 [DX3001]
MC68HC908GR16AVFJE@TQFP32 [DX3001]
MC68HC908GR16CFA@TQFP48 [DX3007]
MC68HC908GR16CFAE@TQFP48 [DX3007]
MC68HC908GR16CFJ@TQFP32 [DX3001]
MC68HC908GR16CFJE@TQFP32 [DX3001]
MC68HC908GR16MFA@TQFP48 [DX3007]
MC68HC908GR16MFAE@TQFP48 [DX3007]
MC68HC908GR16MFJ@TQFP32 [DX3001]
MC68HC908GR16MFJE@TQFP32 [DX3001]
MC68HC908GR16VFA@TQFP48 [DX3007]
MC68HC908GR16VFAE@TQFP48 [DX3007]
MC68HC908GR16VFJ@TQFP32 [DX3001]
MC68HC908GR16VFJE@TQFP32 [DX3001]
MC68HC908GR32ACFA@TQFP48 [DX3007]
MC68HC908GR32ACFAE@TQFP48 [DX3007]
MC68HC908GR32ACFJ@TQFP32 [DX3001]
MC68HC908GR32ACFJE@TQFP32 [DX3001]
MC68HC908GR32ACFU@QFP64 [DX3014]
MC68HC908GR32ACFUE@QFP64 [DX3014]
MC68HC908GR32AMFA@TQFP48 [DX3007]

MC68HC908GR32AMFAE@TQFP48 [DX3007]
MC68HC908GR32AMFJ@TQFP32 [DX3001]
MC68HC908GR32AMFJE@TQFP32 [DX3001]
MC68HC908GR32AMFU@QFP64 [DX3014]
MC68HC908GR32AMFUE@QFP64 [DX3014]
MC68HC908GR32AVFA@TQFP48 [DX3007]
MC68HC908GR32AVFAE@TQFP48 [DX3007]
MC68HC908GR32AVFJ@TQFP32 [DX3001]
MC68HC908GR32AVFJE@TQFP32 [DX3001]
MC68HC908GR32AVFU@QFP64 [DX3014]
MC68HC908GR32AVFUE@QFP64 [DX3014]
MC68HC908GR48ACFA@TQFP48 [DX3007]
MC68HC908GR48ACFAE@TQFP48 [DX3007]
MC68HC908GR48ACFJ@TQFP32 [DX3001]
MC68HC908GR48ACFJE@TQFP32 [DX3001]
MC68HC908GR48ACFU@QFP64 [DX3014]
MC68HC908GR48ACFUE@QFP64 [DX3014]
MC68HC908GR48AMFA@TQFP48 [DX3007]
MC68HC908GR48AMFAE@TQFP48 [DX3007]
MC68HC908GR48AMFJ@TQFP32 [DX3001]
MC68HC908GR48AMFJE@TQFP32 [DX3001]
MC68HC908GR48AMFU@QFP64 [DX3014]
MC68HC908GR48AMFUE@QFP64 [DX3014]
MC68HC908GR48AVFA@TQFP48 [DX3007]
MC68HC908GR48AVFAE@TQFP48 [DX3007]
MC68HC908GR48AVFJ@TQFP32 [DX3001]
MC68HC908GR48AVFJE@TQFP32 [DX3001]
MC68HC908GR48AVFU@QFP64 [DX3014]
MC68HC908GR48AVFUE@QFP64 [DX3014]
MC68HC908GR4ACDW@SOIC28 [DX1033]
MC68HC908GR4ACDWE@SOIC28 [DX1033]
MC68HC908GR4ACFA@TQFP32 [DX3001]
MC68HC908GR4ACFAE@TQFP32 [DX3001]
MC68HC908GR4ACP MC68HC908GR4ACPE
MC68HC908GR4AMDW@SOIC28 [DX1033]
MC68HC908GR4AMDWE@SOIC28 [DX1033]
MC68HC908GR4AMFA@TQFP32 [DX3001]
MC68HC908GR4AMFAE@TQFP32 [DX3001]
MC68HC908GR4AMP MC68HC908GR4AMPE
MC68HC908GR4AVDW@SOIC28 [DX1033]
MC68HC908GR4AVDWE@SOIC28 [DX1033]
MC68HC908GR4AVFA@TQFP32 [DX3001]
MC68HC908GR4AVFAE@TQFP32 [DX3001]
MC68HC908GR4AVP MC68HC908GR4AVPE
MC68HC908GR4CB@SDIP42 [DX0042] MC68HC908GR4CBE@SDIP42 [DX0042]
MC68HC908GR4CDW@SOIC28 [DX1033] MC68HC908GR4CDWE@SOIC28 [DX1033]
MC68HC908GR4CFA@TQFP32 [DX3001] MC68HC908GR4CFAE@TQFP32 [DX3001]
MC68HC908GR4CP MC68HC908GR4CPE

MC68HC908GR4MB@SDIP42 [DX0042]
MC68HC908GR4MBE@SDIP42 [DX0042]
MC68HC908GR4MDW@SOIC28 [DX1033]
MC68HC908GR4MDWE@SOIC28 [DX1033]
MC68HC908GR4MFA@TQFP32 [DX3001]
MC68HC908GR4MFAE@TQFP32 [DX3001]
MC68HC908GR4MP
MC68HC908GR4MPE
MC68HC908GR4VB@SDIP42 [DX0042]
MC68HC908GR4VBE@SDIP42 [DX0042]
MC68HC908GR4VDW@SOIC28 [DX1033]
MC68HC908GR4VDWE@SOIC28 [DX1033]
MC68HC908GR4VFA@TQFP32 [DX3001]
MC68HC908GR4VFAE@TQFP32 [DX3001]
MC68HC908GR4VP
MC68HC908GR4VPE
MC68HC908GR60ACFA@TQFP48 [DX3007]
MC68HC908GR60ACFAE@TQFP48 [DX3007]
MC68HC908GR60ACFJ@TQFP32 [DX3001]
MC68HC908GR60ACFJE@TQFP32 [DX3001]
MC68HC908GR60ACFU@QFP64 [DX3014]
MC68HC908GR60ACFUE@QFP64 [DX3014]
MC68HC908GR60AMFA@TQFP48 [DX3007]
MC68HC908GR60AMFAE@TQFP48 [DX3007]
MC68HC908GR60AMFJ@TQFP32 [DX3001]
MC68HC908GR60AMFJE@TQFP32 [DX3001]
MC68HC908GR60AMFU@QFP64 [DX3014]
MC68HC908GR60AMFUE@QFP64 [DX3014]
MC68HC908GR60AVFA@TQFP48 [DX3007]
MC68HC908GR60AVFAE@TQFP48 [DX3007]
MC68HC908GR60AVFJ@TQFP32 [DX3001]
MC68HC908GR60AVFJE@TQFP32 [DX3001]
MC68HC908GR60AVFU@QFP64 [DX3014]
MC68HC908GR60AVFUE@QFP64 [DX3014]
MC68HC908GR8ACDW@SOIC28 [DX1033]
MC68HC908GR8ACDWE@SOIC28 [DX1033]
MC68HC908GR8ACFA@TQFP32 [DX3001]
MC68HC908GR8ACFAE@TQFP32 [DX3001]
MC68HC908GR8ACP
MC68HC908GR8ACPE
MC68HC908GR8AMDW@SOIC28 [DX1033]
MC68HC908GR8AMDWE@SOIC28 [DX1033]
MC68HC908GR8AMFA@TQFP32 [DX3001]
MC68HC908GR8AMFAE@TQFP32 [DX3001]
MC68HC908GR8AMP
MC68HC908GR8AMPE
MC68HC908GR8AVDW@SOIC28 [DX1033]
MC68HC908GR8AVDWE@SOIC28 [DX1033]
MC68HC908GR8AVFA@TQFP32 [DX3001]
MC68HC908GR8AVFAE@TQFP32 [DX3001]
MC68HC908GR8AVP
MC68HC908GR8AVPE
MC68HC908GR8CB@SDIP42 [DX0042]
MC68HC908GR8CBE@SDIP42 [DX0042]
MC68HC908GR8CDW@SOIC28 [DX1033]
MC68HC908GR8CDWE@SOIC28 [DX1033]
MC68HC908GR8CFA@TQFP32 [DX3001]
MC68HC908GR8CFAE@TQFP32 [DX3001]
MC68HC908GR8CP
MC68HC908GR8CPE
MC68HC908GR8MB@SDIP42 [DX0042]
MC68HC908GR8MBE@SDIP42 [DX0042]
MC68HC908GR8MDW@SOIC28 [DX1033]
MC68HC908GR8MDWE@SOIC28 [DX1033]
MC68HC908GR8MFA@TQFP32 [DX3001]
MC68HC908GR8MFAE@TQFP32 [DX3001]

MC68HC908GR8MP
MC68HC908GR8MPE
MC68HC908GR8VB@SDIP42 [DX0042]
MC68HC908GR8VBE@SDIP42 [DX0042]
MC68HC908GR8VDW@SOIC28 [DX1033]
MC68HC908GR8VDWE@SOIC28 [DX1033]
MC68HC908GR8VFA@TQFP32 [DX3001]
MC68HC908GR8VFAE@TQFP32 [DX3001]
MC68HC908GR8VP
MC68HC908GR8VPE
MC68HC908GT16CB@SDIP42 [DX0042]
MC68HC908GT16CBE@SDIP42 [DX0042]
MC68HC908GT16CFB@TQFP44 [DX3002]
MC68HC908GT16CFBE@TQFP44 [DX3002]
MC68HC908GT16MB@SDIP42 [DX0042]
MC68HC908GT16MBE@SDIP42 [DX0042]
MC68HC908GT16MFB@TQFP44 [DX3002]
MC68HC908GT16MFBE@TQFP44 [DX3002]
MC68HC908GT16VB@SDIP42 [DX0042]
MC68HC908GT16VBE@SDIP42 [DX0042]
MC68HC908GT16VFB@TQFP44 [DX3002]
MC68HC908GT16VFBE@TQFP44 [DX3002]
MC68HC908GT8CB@SDIP42 [DX0042]
MC68HC908GT8CBE@SDIP42 [DX0042]
MC68HC908GT8CFB@TQFP44 [DX3002]
MC68HC908GT8CFBE@TQFP44 [DX3002]
MC68HC908GT8MB@SDIP42 [DX0042]
MC68HC908GT8MBE@SDIP42 [DX0042]
MC68HC908GT8MFB@TQFP44 [DX3002]
MC68HC908GT8MFBE@TQFP44 [DX3002]
MC68HC908GT8VB@SDIP42 [DX0042]
MC68HC908GT8VBE@SDIP42 [DX0042]
MC68HC908GT8VFB@TQFP44 [DX3002]
MC68HC908GT8VFBE@TQFP44 [DX3002]
MC68HC908GZ16CFA@TQFP48 [DX3007]
MC68HC908GZ16CFAE@TQFP48 [DX3007]
MC68HC908GZ16CFJ@TQFP32 [DX3001]
MC68HC908GZ16CFJE@TQFP32 [DX3001]
MC68HC908GZ16MFA@TQFP48 [DX3007]
MC68HC908GZ16MFAE@TQFP48 [DX3007]
MC68HC908GZ16MFJ@TQFP32 [DX3001]
MC68HC908GZ16MFJE@TQFP32 [DX3001]
MC68HC908GZ16VFA@TQFP48 [DX3007]
MC68HC908GZ16VFAE@TQFP48 [DX3007]
MC68HC908GZ16VFJ@TQFP32 [DX3001]
MC68HC908GZ16VFJE@TQFP32 [DX3001]
MC68HC908GZ32CFA@TQFP48 [DX3007]
MC68HC908GZ32CFAE@TQFP48 [DX3007]
MC68HC908GZ32CFJ@TQFP32 [DX3001]
MC68HC908GZ32CFJE@TQFP32 [DX3001]
MC68HC908GZ32CFU@QFP64 [DX3014]
MC68HC908GZ32CFUE@QFP64 [DX3014]
MC68HC908GZ32MFA@TQFP48 [DX3007]
MC68HC908GZ32MFAE@TQFP48 [DX3007]
MC68HC908GZ32MFJ@TQFP32 [DX3001]
MC68HC908GZ32MFJE@TQFP32 [DX3001]
MC68HC908GZ32MFU@QFP64 [DX3014]
MC68HC908GZ32MFUE@QFP64 [DX3014]
MC68HC908GZ32VFA@TQFP48 [DX3007]
MC68HC908GZ32VFAE@TQFP48 [DX3007]
MC68HC908GZ32VFJ@TQFP32 [DX3001]
MC68HC908GZ32VFJE@TQFP32 [DX3001]
MC68HC908GZ32VFU@QFP64 [DX3014]
MC68HC908GZ32VFUE@QFP64 [DX3014]
MC68HC908GZ48CFA@TQFP48 [DX3007]

MC68HC908GZ48CFAE@TQFP48 [DX3007]
MC68HC908GZ48CFJ@TQFP32 [DX3001]
MC68HC908GZ48CFJE@TQFP32 [DX3001]
MC68HC908GZ48CFU@QFP64 [DX3014]
MC68HC908GZ48CFUE@QFP64 [DX3014]
MC68HC908GZ48MFA@TQFP48 [DX3007]
MC68HC908GZ48MFAE@TQFP48 [DX3007]
MC68HC908GZ48MFJ@TQFP32 [DX3001]
MC68HC908GZ48MFJE@TQFP32 [DX3001]
MC68HC908GZ48MFU@QFP64 [DX3014]
MC68HC908GZ48MFUE@QFP64 [DX3014]
MC68HC908GZ48VFA@TQFP48 [DX3007]
MC68HC908GZ48VFAE@TQFP48 [DX3007]
MC68HC908GZ48VFJ@TQFP32 [DX3001]
MC68HC908GZ48VFJE@TQFP32 [DX3001]
MC68HC908GZ48VFU@QFP64 [DX3014]
MC68HC908GZ48VFUE@QFP64 [DX3014]
MC68HC908GZ60CFA@TQFP48 [DX3007]
MC68HC908GZ60CFAE@TQFP48 [DX3007]
MC68HC908GZ60CFJ@TQFP32 [DX3001]
MC68HC908GZ60CFJE@TQFP32 [DX3001]
MC68HC908GZ60CFU@QFP64 [DX3014]
MC68HC908GZ60CFUE@QFP64 [DX3014]
MC68HC908GZ60MFA@TQFP48 [DX3007]
MC68HC908GZ60MFAE@TQFP48 [DX3007]
MC68HC908GZ60MFJ@TQFP32 [DX3001]
MC68HC908GZ60MFJE@TQFP32 [DX3001]
MC68HC908GZ60MFU@QFP64 [DX3014]
MC68HC908GZ60MFUE@QFP64 [DX3014]
MC68HC908GZ60VFA@TQFP48 [DX3007]
MC68HC908GZ60VFAE@TQFP48 [DX3007]
MC68HC908GZ60VFJ@TQFP32 [DX3001]
MC68HC908GZ60VFJE@TQFP32 [DX3001]
MC68HC908GZ60VFU@QFP64 [DX3014]
MC68HC908GZ60VFUE@QFP64 [DX3014]
MC68HC908GZ8CFA@TQFP48 [DX3007]
MC68HC908GZ8CFAE@TQFP48 [DX3007]
MC68HC908GZ8CFJ@TQFP32 [DX3001]
MC68HC908GZ8CFJE@TQFP32 [DX3001]
MC68HC908GZ8MFA@TQFP48 [DX3007]
MC68HC908GZ8MFAE@TQFP48 [DX3007]
MC68HC908GZ8MFJ@TQFP32 [DX3001]
MC68HC908GZ8MFJE@TQFP32 [DX3001]
MC68HC908GZ8VFA@TQFP48 [DX3007]
MC68HC908GZ8VFAE@TQFP48 [DX3007]
MC68HC908GZ8VFJ@TQFP32 [DX3001]
MC68HC908GZ8VFJE@TQFP32 [DX3001]
MC68HC908JB12DW@SOIC28 [DX1033]
MC68HC908JB12DWE@SOIC28 [DX1033]
MC68HC908JB12JDW@SOIC20 [DX1033]
MC68HC908JB12JDWE@SOIC20 [DX1033]
MC68HC908JB16DW@SOIC28 [DX1033]
MC68HC908JB16DWE@SOIC28 [DX1033]
MC68HC908JB16FA@QFP32 [DX3001]
MC68HC908JB16FAE@QFP32 [DX3001]
MC68HC908JB16JDW@SOIC20 [DX1033]
MC68HC908JB16JDWE@SOIC20 [DX1033]
MC68HC908JB8ADW@SOIC28 [DX1033]
MC68HC908JB8ADWE@SOIC28 [DX1033]
MC68HC908JB8FB@TQFP44 [DX3003]
MC68HC908JB8FBE@TQFP44 [DX3003]
MC68HC908JB8JDW@SOIC20 [DX1033]
MC68HC908JB8JDWE@SOIC20 [DX1033]
MC68HC908JB8JP
MC68HC908JB8JPE
MC68HC908JK1CDW@SOIC20 [DX1033]
MC68HC908JK1CDWE@SOIC20 [DX1033]
MC68HC908JK1CP
MC68HC908JK1CPE

MC68HC908JK1ECDW@SOIC20 [DX1033]
MC68HC908JK1ECDWE@SOIC20 [DX1033]
MC68HC908JK1ECP MC68HC908JK1ECPE
MC68HC908JK1EMDW@SOIC20 [DX1033]
MC68HC908JK1EMDWE@SOIC20 [DX1033]
MC68HC908JK1EMP MC68HC908JK1EMPE
MC68HC908JK1EVDW@SOIC20 [DX1033]
MC68HC908JK1EVDWE@SOIC20 [DX1033]
MC68HC908JK1EVP MC68HC908JK1EVPE
MC68HC908JK1MDW@SOIC20 [DX1033] MC68HC908JK1MDWE@SOIC20 [DX1033]
MC68HC908JK1MP MC68HC908JK1MPE
MC68HC908JK1VDW@SOIC20 [DX1033] MC68HC908JK1VDWE@SOIC20 [DX1033]
MC68HC908JK1VP MC68HC908JK1VPE
MC68HC908JK3CDW@SOIC20 [DX1033] MC68HC908JK3CDWE@SOIC20 [DX1033]
MC68HC908JK3CP MC68HC908JK3CPE
MC68HC908JK3ECDW@SOIC20 [DX1033]
MC68HC908JK3ECDWE@SOIC20 [DX1033]
MC68HC908JK3ECP MC68HC908JK3ECPE
MC68HC908JK3EMDW@SOIC20 [DX1033]
MC68HC908JK3EMDWE@SOIC20 [DX1033]
MC68HC908JK3EMP MC68HC908JK3EMPE
MC68HC908JK3EVDW@SOIC20 [DX1033]
MC68HC908JK3EVDWE@SOIC20 [DX1033]
MC68HC908JK3EVP MC68HC908JK3EVPE
MC68HC908JK3MDW@SOIC20 [DX1033] MC68HC908JK3MDWE@SOIC20 [DX1033]
MC68HC908JK3MP MC68HC908JK3MPE
MC68HC908JK3VDW@SOIC20 [DX1033] MC68HC908JK3VDWE@SOIC20 [DX1033]
MC68HC908JK3VP MC68HC908JK3VPE
MC68HC908JK8CDW@SOIC20 [DX1033] MC68HC908JK8CDWE@SOIC20 [DX1033]
MC68HC908JK8CP MC68HC908JK8CPE
MC68HC908JK8MDW@SOIC20 [DX1033] MC68HC908JK8MDWE@SOIC20 [DX1033]
MC68HC908JK8MP MC68HC908JK8MPE
MC68HC908JK8VDW@SOIC20 [DX1033] MC68HC908JK8VDWE@SOIC20 [DX1033]
MC68HC908JK8VP MC68HC908JK8VPE
MC68HC908JL16CDW@SOIC28 [DX1033]
MC68HC908JL16CDWE@SOIC28 [DX1033]
MC68HC908JL16CFJ@TQFP32 [DX3001]
MC68HC908JL16CFJE@TQFP32 [DX3001]
MC68HC908JL16CP MC68HC908JL16CPE
MC68HC908JL16CSP@SDIP32 [DX0032]
MC68HC908JL16CSPE@SDIP32 [DX0032]
MC68HC908JL16MDW@SOIC28 [DX1033]
MC68HC908JL16MDWE@SOIC28 [DX1033]
MC68HC908JL16MFJ@TQFP32 [DX3001]
MC68HC908JL16MFJE@TQFP32 [DX3001]
MC68HC908JL16MP MC68HC908JL16MPE
MC68HC908JL16MSP@SDIP32 [DX0032]
MC68HC908JL16MSPE@SDIP32 [DX0032]

MC68HC908JL16VDW@SOIC28 [DX1033]
MC68HC908JL16VDWE@SOIC28 [DX1033]
MC68HC908JL16VFJ@TQFP32 [DX3001]
MC68HC908JL16VFJE@TQFP32 [DX3001]
MC68HC908JL16VP MC68HC908JL16VPE
MC68HC908JL16VSP@SDIP32 [DX0032]
MC68HC908JL16VSPE@SDIP32 [DX0032]
MC68HC908JL3CDW@SOIC28 [DX1033] MC68HC908JL3CDWE@SOIC28 [DX1033]
MC68HC908JL3CP MC68HC908JL3CPE
MC68HC908JL3ECDW@SOIC28 [DX1033]
MC68HC908JL3ECDWE@SOIC28 [DX1033]
MC68HC908JL3ECFA@TQFP48 [DX3007]
MC68HC908JL3ECFAE@TQFP48 [DX3007]
MC68HC908JL3ECP MC68HC908JL3ECPE
MC68HC908JL3EMDW@SOIC28 [DX1033]
MC68HC908JL3EMDWE@SOIC28 [DX1033]
MC68HC908JL3EMFA@TQFP48 [DX3007]
MC68HC908JL3EMFAE@TQFP48 [DX3007]
MC68HC908JL3EMP MC68HC908JL3EMPE
MC68HC908JL3EVDW@SOIC28 [DX1033]
MC68HC908JL3EVDWE@SOIC28 [DX1033]
MC68HC908JL3EVFA@TQFP48 [DX3007]
MC68HC908JL3EVFAE@TQFP48 [DX3007]
MC68HC908JL3EVP MC68HC908JL3EVPE
MC68HC908JL3MDW@SOIC28 [DX1033] MC68HC908JL3MDWE@SOIC28 [DX1033]
MC68HC908JL3MP MC68HC908JL3MPE
MC68HC908JL3VDW@SOIC28 [DX1033] MC68HC908JL3VDWE@SOIC28 [DX1033]
MC68HC908JL3VP MC68HC908JL3VPE
MC68HC908JL8CDW@SOIC28 [DX1033] MC68HC908JL8CDWE@SOIC28 [DX1033]
MC68HC908JL8CFA@TQFP32 [DX3001] MC68HC908JL8CFAE@TQFP32 [DX3001]
MC68HC908JL8CP MC68HC908JL8CPE
MC68HC908JL8CSP@SDIP32 [DX0032] MC68HC908JL8CSPE@SDIP32 [DX0032]
MC68HC908JL8MDW@SOIC28 [DX1033] MC68HC908JL8MDWE@SOIC28 [DX1033]
MC68HC908JL8MFA@TQFP32 [DX3001] MC68HC908JL8MFAE@TQFP32 [DX3001]
MC68HC908JL8MP MC68HC908JL8MPE
MC68HC908JL8MSP@SDIP32 [DX0032] MC68HC908JL8MSPE@SDIP32 [DX0032]
MC68HC908JL8VDW@SOIC28 [DX1033] MC68HC908JL8VDWE@SOIC28 [DX1033]
MC68HC908JL8VFA@TQFP32 [DX3001] MC68HC908JL8VFAE@TQFP32 [DX3001]
MC68HC908JL8VP MC68HC908JL8VPE
MC68HC908JL8VSP@SDIP32 [DX0032] MC68HC908JL8VSPE@SDIP32 [DX0032]
MC68HC908KK3ECDW@SOIC20 [DX1033]
MC68HC908KK3ECDWE@SOIC20 [DX1033]
MC68HC908KK3ECP MC68HC908KK3ECPE
MC68HC908KK3EMDW@SOIC20 [DX1033]
MC68HC908KK3EMDWE@SOIC20 [DX1033]
MC68HC908KK3EMP MC68HC908KK3EMPE
MC68HC908KK3EVDW@SOIC20 [DX1033]
MC68HC908KK3EVDWE@SOIC20 [DX1033]

MC68HC908KK3EVP	MC68HC908KK3EVPE
MC68HC908KL3ECDW@SOIC28 [DX1033]	
MC68HC908KL3ECDWE@SOIC28 [DX1033]	
MC68HC908KL3ECP	MC68HC908KL3ECPE
MC68HC908KL3EMDW@SOIC28 [DX1033]	
MC68HC908KL3EMDWE@SOIC28 [DX1033]	
MC68HC908KL3EMP	MC68HC908KL3EMPE
MC68HC908KL3EVDW@SOIC28 [DX1033]	
MC68HC908KL3EVDWE@SOIC28 [DX1033]	
MC68HC908KL3EVP	MC68HC908KL3EVPE
MC68HC908KL8CDW@SOIC28 [DX1033]	MC68HC908KL8CDWE@SOIC28 [DX1033]
MC68HC908KL8CP	MC68HC908KL8CPE
MC68HC908KL8CSP@SDIP32 [DX0032]	MC68HC908KL8CSPE@SDIP32 [DX0032]
MC68HC908KL8MDW@SOIC28 [DX1033]	MC68HC908KL8MDWE@SOIC28 [DX1033]
MC68HC908KL8MP	MC68HC908KL8MPE
MC68HC908KL8MSP@SDIP32 [DX0032]	MC68HC908KL8MSPE@SDIP32 [DX0032]
MC68HC908KL8VDW@SOIC28 [DX1033]	MC68HC908KL8VDWE@SOIC28 [DX1033]
MC68HC908KL8VP	MC68HC908KL8VPE
MC68HC908KL8VSP@SDIP32 [DX0032]	MC68HC908KL8VSPE@SDIP32 [DX0032]
MC68HC908KX2CDW@SOIC16 [DX1033]	MC68HC908KX2CDWE@SOIC16 [DX1033]
MC68HC908KX2CP	MC68HC908KX2CPE
MC68HC908KX2MDW@SOIC16 [DX1033]	MC68HC908KX2MDWE@SOIC16 [DX1033]
MC68HC908KX2MP	MC68HC908KX2MPE
MC68HC908KX2VDW@SOIC16 [DX1033]	MC68HC908KX2VDWE@SOIC16 [DX1033]
MC68HC908KX8CDW@SOIC16 [DX1033]	MC68HC908KX8CDWE@SOIC16 [DX1033]
MC68HC908KX8CP	MC68HC908KX8CPE
MC68HC908KX8MDW@SOIC16 [DX1033]	MC68HC908KX8MDWE@SOIC16 [DX1033]
MC68HC908KX8MP	MC68HC908KX8MPE
MC68HC908KX8VDW@SOIC16 [DX1033]	MC68HC908KX8VDWE@SOIC16 [DX1033]
MC68HC908KX8VP	MC68HC908KX8VPE
MC68HC908KXVMP	MC68HC908KXVMPE
MC68HC908LB8CDW@SOIC20 [DX1033]	MC68HC908LB8CDWE@SOIC20 [DX1033]
MC68HC908LB8CP	MC68HC908LB8CPE
MC68HC908LB8MDW@SOIC20 [DX1033]	MC68HC908LB8MDWE@SOIC20 [DX1033]
MC68HC908LB8MP	MC68HC908LB8MPE
MC68HC908LB8VDW@SOIC20 [DX1033]	MC68HC908LB8VDWE@SOIC20 [DX1033]
MC68HC908LB8VP	MC68HC908LB8VPE
MC68HC908LD60IFU@QFP64 [DX3014]	MC68HC908LD64IFU@QFP64 [DX3014]
MC68HC908LJ12CFB@TQFP52 [DX3010]	
MC68HC908LJ12CFBE@TQFP52 [DX3010]	
MC68HC908LJ12CFU@TQFP64 [DX3014]	
MC68HC908LJ12CFUE@TQFP64 [DX3014]	
MC68HC908LJ12CPB@TQFP64 [DX3011]	
MC68HC908LJ12CPBE@TQFP64 [DX3011]	
MC68HC908LJ12MFB@TQFP52 [DX3010]	
MC68HC908LJ12MFBE@TQFP52 [DX3010]	
MC68HC908LJ12MFU@TQFP64 [DX3014]	
MC68HC908LJ12MFUE@TQFP64 [DX3014]	

MC68HC908LJ12MPB@TQFP64 [DX3011]
MC68HC908LJ12MPBE@TQFP64 [DX3011]
MC68HC908LJ12VFB@TQFP52 [DX3010]
MC68HC908LJ12VFBE@TQFP52 [DX3010]
MC68HC908LJ12VFU@TQFP64 [DX3014]
MC68HC908LJ12VFUE@TQFP64 [DX3014]
MC68HC908LJ12VPB@TQFP64 [DX3011]
MC68HC908LJ12VPBE@TQFP64 [DX3011]
MC68HC908LJ24CFQ@TQFP80 [DX3018]
MC68HC908LJ24CFQE@TQFP80 [DX3018]
MC68HC908LJ24CFU@TQFP64 [DX3014]
MC68HC908LJ24CFUE@TQFP64 [DX3014]
MC68HC908LJ24CPB@TQFP64 [DX3011]
MC68HC908LJ24CPBE@TQFP64 [DX3011]
MC68HC908LJ24CPK@TQFP80 [DX3016]
MC68HC908LJ24CPKE@TQFP80 [DX3016]
MC68HC908LJ24MFQ@TQFP80 [DX3018]
MC68HC908LJ24MFQE@TQFP80 [DX3018]
MC68HC908LJ24MFU@TQFP64 [DX3014]
MC68HC908LJ24MFUE@TQFP64 [DX3014]
MC68HC908LJ24MPB@TQFP64 [DX3011]
MC68HC908LJ24MPBE@TQFP64 [DX3011]
MC68HC908LJ24MPK@TQFP80 [DX3016]
MC68HC908LJ24MPKE@TQFP80 [DX3016]
MC68HC908LJ24VFQ@TQFP80 [DX3018]
MC68HC908LJ24VFQE@TQFP80 [DX3018]
MC68HC908LJ24VFU@TQFP64 [DX3014]
MC68HC908LJ24VFUE@TQFP64 [DX3014]
MC68HC908LJ24VPB@TQFP64 [DX3011]
MC68HC908LJ24VPBE@TQFP64 [DX3011]
MC68HC908LJ24VPK@TQFP80 [DX3016]
MC68HC908LJ24VPKE@TQFP80 [DX3016]
MC68HC908LK24CFQ@TQFP80 [DX3018]
MC68HC908LK24CFQE@TQFP80 [DX3018]
MC68HC908LK24CFU@TQFP64 [DX3014]
MC68HC908LK24CFUE@TQFP64 [DX3014]
MC68HC908LK24CPB@TQFP64 [DX3011]
MC68HC908LK24CPBE@TQFP64 [DX3011]
MC68HC908LK24CPK@TQFP80 [DX3016]
MC68HC908LK24CPKE@TQFP80 [DX3016]
MC68HC908LK24MFQ@TQFP80 [DX3018]
MC68HC908LK24MFQE@TQFP80 [DX3018]
MC68HC908LK24MFU@TQFP64 [DX3014]
MC68HC908LK24MFUE@TQFP64 [DX3014]
MC68HC908LK24MPB@TQFP64 [DX3011]
MC68HC908LK24MPBE@TQFP64 [DX3011]
MC68HC908LK24MPK@TQFP80 [DX3016]
MC68HC908LK24MPKE@TQFP80 [DX3016]

MC68HC908LK24VFQ@TQFP80 [DX3018]
MC68HC908LK24VFQE@TQFP80 [DX3018]
MC68HC908LK24VFU@TQFP64 [DX3014]
MC68HC908LK24VFUE@TQFP64 [DX3014]
MC68HC908LK24VPB@TQFP64 [DX3011]
MC68HC908LK24VPBE@TQFP64 [DX3011]
MC68HC908LK24VPK@TQFP80 [DX3016]
MC68HC908LK24VPKE@TQFP80 [DX3016]
MC68HC908LV8CPB@TQFP52 [DX3010] MC68HC908LV8CPBE@TQFP52 [DX3010]
MC68HC908MR16CB@SDIP56 [DX0056] MC68HC908MR16CBE@SDIP56 [DX0056]
MC68HC908MR16CFU@TQFP64 [DX3014]
MC68HC908MR16CFUE@TQFP64 [DX3014]
MC68HC908MR16MB@SDIP56 [DX0056] MC68HC908MR16MBE@SDIP56 [DX0056]
MC68HC908MR16MFU@TQFP64 [DX3014]
MC68HC908MR16MFUE@TQFP64 [DX3014]
MC68HC908MR16VB@SDIP56 [DX0056] MC68HC908MR16VBE@SDIP56 [DX0056]
MC68HC908MR16VFU@TQFP64 [DX3014]
MC68HC908MR16VFUE@TQFP64 [DX3014]
MC68HC908MR32CB@SDIP56 [DX0056] MC68HC908MR32CBE@SDIP56 [DX0056]
MC68HC908MR32CFU@TQFP64 [DX3014]
MC68HC908MR32CFUE@TQFP64 [DX3014]
MC68HC908MR32MB@SDIP56 [DX0056] MC68HC908MR32MBE@SDIP56 [DX0056]
MC68HC908MR32MFU@TQFP64 [DX3014]
MC68HC908MR32MFUE@TQFP64 [DX3014]
MC68HC908MR32VB@SDIP56 [DX0056] MC68HC908MR32VBE@SDIP56 [DX0056]
MC68HC908MR32VFU@TQFP64 [DX3014]
MC68HC908MR32VFUE@TQFP64 [DX3014]
MC68HC908MR8CDW@SOIC28 [DX1033] MC68HC908MR8CDWE@SOIC28 [DX1033]
MC68HC908MR8CFA@QFP32 [DX3001] MC68HC908MR8CFAE@QFP32 [DX3001]
MC68HC908MR8CP MC68HC908MR8CPE
MC68HC908MR8MDW@SOIC28 [DX1033] MC68HC908MR8MDWE@SOIC28 [DX1033]
MC68HC908MR8MFA@QFP32 [DX3001] MC68HC908MR8MFAE@QFP32 [DX3001]
MC68HC908MR8MP MC68HC908MR8MPE
MC68HC908MR8VDW@SOIC28 [DX1033] MC68HC908MR8VDWE@SOIC28 [DX1033]
MC68HC908MR8VFA@QFP32 [DX3001] MC68HC908MR8VFAE@QFP32 [DX3001]
MC68HC908MR8VP MC68HC908MR8VPE
MC68HC908QB4CDT@TSSOP16 [DX1001]
MC68HC908QB4CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB4CDTE@TSSOP16 [DX1001]
MC68HC908QB4CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4CDW@SOIC16 [DX1072]
MC68HC908QB4CDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4CDWE@SOIC16 [DX1072]
MC68HC908QB4CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4CP MC68HC908QB4CP(a-trim)
MC68HC908QB4CPE MC68HC908QB4CPE(a-trim)
MC68HC908QB4MDT@TSSOP16 [DX1001]
MC68HC908QB4MDT@TSSOP16(a-trim) [DX1001]

MC68HC908QB4MDTE@TSSOP16 [DX1001]
MC68HC908QB4MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4MDW@SOIC16 [DX1072]
MC68HC908QB4MDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4MDWE@SOIC16 [DX1072]
MC68HC908QB4MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4MP MC68HC908QB4MP(a-trim)
MC68HC908QB4MPE MC68HC908QB4MPE(a-trim)
MC68HC908QB4VDT@TSSOP16 [DX1001]
MC68HC908QB4VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB4VDTE@TSSOP16 [DX1001]
MC68HC908QB4VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4VDW@SOIC16 [DX1072]
MC68HC908QB4VDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4VDWE@SOIC16 [DX1072]
MC68HC908QB4VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4VP MC68HC908QB4VP(a-trim)
MC68HC908QB4VPE MC68HC908QB4VPE(a-trim)
MC68HC908QB8CDT@TSSOP16 [DX1001]
MC68HC908QB8CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB8CDTE@TSSOP16 [DX1001]
MC68HC908QB8CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8CDW@SOIC16 [DX1072]
MC68HC908QB8CDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8CDWE@SOIC16 [DX1072]
MC68HC908QB8CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8CP MC68HC908QB8CP(a-trim)
MC68HC908QB8CPE MC68HC908QB8CPE(a-trim)
MC68HC908QB8MDT@TSSOP16 [DX1001]
MC68HC908QB8MDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB8MDTE@TSSOP16 [DX1001]
MC68HC908QB8MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8MDW@SOIC16 [DX1072]
MC68HC908QB8MDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8MDWE@SOIC16 [DX1072]
MC68HC908QB8MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8MP MC68HC908QB8MP(a-trim)
MC68HC908QB8MPE MC68HC908QB8MPE(a-trim)
MC68HC908QB8VDT@TSSOP16 [DX1001]
MC68HC908QB8VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB8VDTE@TSSOP16 [DX1001]
MC68HC908QB8VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8VDW@SOIC16 [DX1072]
MC68HC908QB8VDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8VDWE@SOIC16 [DX1072]
MC68HC908QB8VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8VP MC68HC908QB8VP(a-trim)
MC68HC908QB8VPE MC68HC908QB8VPE(a-trim)

MC68HC908QC16CDR@TSSOP28 [DX1001]
MC68HC908QC16CDRE@TSSOP28 [DX1001]
MC68HC908QC16CDS@TSSOP20 [DX1001]
MC68HC908QC16CDSE@TSSOP20 [DX1001]
MC68HC908QC16CDT@TSSOP16 [DX1001]
MC68HC908QC16CDTE@TSSOP16 [DX1001]
MC68HC908QC16CDX@SOIC16 [DX1072]
MC68HC908QC16CDXE@SOIC16 [DX1072]
MC68HC908QC16CDY@SOIC20 [DX1033]
MC68HC908QC16CDYE@SOIC20 [DX1033]
MC68HC908QC16CDZ@SOIC28 [DX1033]
MC68HC908QC16CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16CDZE@SOIC28 [DX1033]
MC68HC908QC16CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC16MDR@TSSOP28 [DX1001]
MC68HC908QC16MDRE@TSSOP28 [DX1001]
MC68HC908QC16MDS@TSSOP20 [DX1001]
MC68HC908QC16MDSE@TSSOP20 [DX1001]
MC68HC908QC16MDT@TSSOP16 [DX1001]
MC68HC908QC16MDTE@TSSOP16 [DX1001]
MC68HC908QC16MDX@SOIC16 [DX1072]
MC68HC908QC16MDXE@SOIC16 [DX1072]
MC68HC908QC16MDY@SOIC20 [DX1033]
MC68HC908QC16MDYE@SOIC20 [DX1033]
MC68HC908QC16MDZ@SOIC28 [DX1033]
MC68HC908QC16MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16MDZE@SOIC28 [DX1033]
MC68HC908QC16MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC16VDR@TSSOP28 [DX1001]
MC68HC908QC16VDRE@TSSOP28 [DX1001]
MC68HC908QC16VDS@TSSOP20 [DX1001]
MC68HC908QC16VDSE@TSSOP20 [DX1001]
MC68HC908QC16VDT@TSSOP16 [DX1001]
MC68HC908QC16VDTE@TSSOP16 [DX1001]
MC68HC908QC16VDX@SOIC16 [DX1072]
MC68HC908QC16VDXE@SOIC16 [DX1072]
MC68HC908QC16VDY@SOIC20 [DX1033]
MC68HC908QC16VDYE@SOIC20 [DX1033]
MC68HC908QC16VDZ@SOIC28 [DX1033]
MC68HC908QC16VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16VDZE@SOIC28 [DX1033]
MC68HC908QC16VDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4CDR@TSSOP28 [DX1001]
MC68HC908QC4CDRE@TSSOP28 [DX1001]
MC68HC908QC4CDS@TSSOP20 [DX1001]
MC68HC908QC4CDSE@TSSOP20 [DX1001]
MC68HC908QC4CDT@TSSOP16 [DX1001]
MC68HC908QC4CDTE@TSSOP16 [DX1001]

MC68HC908QC4CDX@SOIC16 [DX1072]　　MC68HC908QC4CDXE@SOIC16 [DX1072]
MC68HC908QC4CDY@SOIC20 [DX1033]　　MC68HC908QC4CDYE@SOIC20 [DX1033]
MC68HC908QC4CDZ@SOIC28 [DX1033]
MC68HC908QC4CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4CDZE@SOIC28 [DX1033]
MC68HC908QC4CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4MDR@TSSOP28 [DX1001]
MC68HC908QC4MDRE@TSSOP28 [DX1001]
MC68HC908QC4MDS@TSSOP20 [DX1001]
MC68HC908QC4MDSE@TSSOP20 [DX1001]
MC68HC908QC4MDT@TSSOP16 [DX1001]
MC68HC908QC4MDTE@TSSOP16 [DX1001]
MC68HC908QC4MDX@SOIC16 [DX1072]　　MC68HC908QC4MDXE@SOIC16 [DX1072]
MC68HC908QC4MDY@SOIC20 [DX1033]　　MC68HC908QC4MDYE@SOIC20 [DX1033]
MC68HC908QC4MDZ@SOIC28 [DX1033]
MC68HC908QC4MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4MDZE@SOIC28 [DX1033]
MC68HC908QC4MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4VDR@TSSOP28 [DX1001]
MC68HC908QC4VDRE@TSSOP28 [DX1001]
MC68HC908QC4VDS@TSSOP20 [DX1001]
MC68HC908QC4VDSE@TSSOP20 [DX1001]
MC68HC908QC4VDT@TSSOP16 [DX1001]
MC68HC908QC4VDTE@TSSOP16 [DX1001]
MC68HC908QC4VDX@SOIC16 [DX1072]　　MC68HC908QC4VDXE@SOIC16 [DX1072]
MC68HC908QC4VDY@SOIC20 [DX1033]　　MC68HC908QC4VDYE@SOIC20 [DX1033]
MC68HC908QC4VDZ@SOIC28 [DX1033]
MC68HC908QC4VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4VDZE@SOIC28 [DX1033]
MC68HC908QC4VDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC8CDR@TSSOP28 [DX1001]
MC68HC908QC8CDRE@TSSOP28 [DX1001]
MC68HC908QC8CDS@TSSOP20 [DX1001]
MC68HC908QC8CDSE@TSSOP20 [DX1001]
MC68HC908QC8CDT@TSSOP16 [DX1001]
MC68HC908QC8CDTE@TSSOP16 [DX1001]
MC68HC908QC8CDX@SOIC16 [DX1072]　　MC68HC908QC8CDXE@SOIC16 [DX1072]
MC68HC908QC8CDY@SOIC20 [DX1033]　　MC68HC908QC8CDYE@SOIC20 [DX1033]
MC68HC908QC8CDZ@SOIC28 [DX1033]
MC68HC908QC8CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8CDZE@SOIC28 [DX1033]
MC68HC908QC8CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC8MDR@TSSOP28 [DX1001]
MC68HC908QC8MDRE@TSSOP28 [DX1001]
MC68HC908QC8MDS@TSSOP20 [DX1001]
MC68HC908QC8MDSE@TSSOP20 [DX1001]
MC68HC908QC8MDT@TSSOP16 [DX1001]
MC68HC908QC8MDTE@TSSOP16 [DX1001]

MC68HC908QC8MDX@SOIC16 [DX1072]　　MC68HC908QC8MDXE@SOIC16 [DX1072]
MC68HC908QC8MDY@SOIC20 [DX1033]　　MC68HC908QC8MDYE@SOIC20 [DX1033]
MC68HC908QC8MDZ@SOIC28 [DX1033]
MC68HC908QC8MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8MDZE@SOIC28 [DX1033]
MC68HC908QC8MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC8VDR@TSSOP28 [DX1001]
MC68HC908QC8VDRE@TSSOP28 [DX1001]
MC68HC908QC8VDS@TSSOP20 [DX1001]
MC68HC908QC8VDSE@TSSOP20 [DX1001]
MC68HC908QC8VDT@TSSOP16 [DX1001]
MC68HC908QC8VDTE@TSSOP16 [DX1001]
MC68HC908QC8VDX@SOIC16 [DX1072]　　MC68HC908QC8VDXE@SOIC16 [DX1072]
MC68HC908QC8VDY@SOIC20 [DX1033]　　MC68HC908QC8VDYE@SOIC20 [DX1033]
MC68HC908QC8VDZ@SOIC28 [DX1033]
MC68HC908QC8VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8VDZE@SOIC28 [DX1033]
MC68HC908QC8VDZE@SOIC28(a-trim) [DX1033]
MC68HC908QF4CFJ@QFP32 [DX3001]　　MC68HC908QF4CFJE@QFP32 [DX3001]
MC68HC908QF4MFJ@QFP32 [DX3001]　　MC68HC908QF4MFJE@QFP32 [DX3001]
MC68HC908QF4VFJ@QFP32 [DX3001]　　MC68HC908QF4VFJE@QFP32 [DX3001]
MC68HC908QL2CDT@TSSOP16 [DX1001]
MC68HC908QL2CDTE@TSSOP16 [DX1001]
MC68HC908QL2CDW@SOIC16 [DX1032]　　MC68HC908QL2CDWE@SOIC16 [DX1032]
MC68HC908QL2MDT@TSSOP16 [DX1001]
MC68HC908QL2MDTE@TSSOP16 [DX1001]
MC68HC908QL2MDW@SOIC16 [DX1032]　　MC68HC908QL2MDWE@SOIC16 [DX1032]
MC68HC908QL2VDT@TSSOP16 [DX1001]
MC68HC908QL2VDTE@TSSOP16 [DX1001]
MC68HC908QL2VDW@SOIC16 [DX1032]　　MC68HC908QL2VDWE@SOIC16 [DX1032]
MC68HC908QL3CDT@TSSOP16 [DX1001]
MC68HC908QL3CDTE@TSSOP16 [DX1001]
MC68HC908QL3CDW@SOIC16 [DX1032]　　MC68HC908QL3CDWE@SOIC16 [DX1032]
MC68HC908QL3MDT@TSSOP16 [DX1001]
MC68HC908QL3MDTE@TSSOP16 [DX1001]
MC68HC908QL3MDW@SOIC16 [DX1032]　　MC68HC908QL3MDWE@SOIC16 [DX1032]
MC68HC908QL3VDT@TSSOP16 [DX1001]
MC68HC908QL3VDTE@TSSOP16 [DX1001]
MC68HC908QL3VDW@SOIC16 [DX1032]　　MC68HC908QL3VDWE@SOIC16 [DX1032]
MC68HC908QL4CDT@TSSOP16 [DX1001]
MC68HC908QL4CDTE@TSSOP16 [DX1001]
MC68HC908QL4CDW@SOIC16 [DX1032]　　MC68HC908QL4CDWE@SOIC16 [DX1032]
MC68HC908QL4MDT@TSSOP16 [DX1001]
MC68HC908QL4MDTE@TSSOP16 [DX1001]
MC68HC908QL4MDW@SOIC16 [DX1032]　　MC68HC908QL4MDWE@SOIC16 [DX1032]
MC68HC908QL4VDT@TSSOP16 [DX1001]
MC68HC908QL4VDTE@TSSOP16 [DX1001]
MC68HC908QL4VDW@SOIC16 [DX1032]　　MC68HC908QL4VDWE@SOIC16 [DX1032]

MC68HC908QT1ACDW@SOIC8 [DX1032]
MC68HC908QT1ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1ACDWE@SOIC8 [DX1032]
MC68HC908QT1ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1ACFQ@DFN8 [DX4004]
MC68HC908QT1ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1ACFQE@DFN8 [DX4004]
MC68HC908QT1ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1ACP MC68HC908QT1ACP(a-trim)
MC68HC908QT1ACPE MC68HC908QT1ACPE(a-trim)
MC68HC908QT1AMDW@SOIC8 [DX1032]
MC68HC908QT1AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1AMDWE@SOIC8 [DX1032]
MC68HC908QT1AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1AMFQ@DFN8 [DX4004]
MC68HC908QT1AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1AMFQE@DFN8 [DX4004]
MC68HC908QT1AMFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1AMP MC68HC908QT1AMP(a-trim)
MC68HC908QT1AMPE MC68HC908QT1AMPE(a-trim)
MC68HC908QT1AVDW@SOIC8 [DX1032]
MC68HC908QT1AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1AVDWE@SOIC8 [DX1032]
MC68HC908QT1AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1AVFQ@DFN8 [DX4004]
MC68HC908QT1AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1AVFQE@DFN8 [DX4004]
MC68HC908QT1AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1AVP MC68HC908QT1AVP(a-trim)
MC68HC908QT1AVPE MC68HC908QT1AVPE(a-trim)
MC68HC908QT1CDW@SOIC8 [DX1032] MC68HC908QT1CDWE@SOIC8 [DX1032]
MC68HC908QT1CFQ@DFN8 [DX4004] MC68HC908QT1CFQE@DFN8 [DX4004]
MC68HC908QT1CP MC68HC908QT1CPE
MC68HC908QT1MDW@SOIC8 [DX1032] MC68HC908QT1MDWE@SOIC8 [DX1032]
MC68HC908QT1MFQ@DFN8 [DX4004] MC68HC908QT1MFQE@DFN8 [DX4004]
MC68HC908QT1MP MC68HC908QT1MPE
MC68HC908QT1VDW@SOIC8 [DX1032] MC68HC908QT1VDWE@SOIC8 [DX1032]
MC68HC908QT1VFQ@DFN8 [DX4004] MC68HC908QT1VFQE@DFN8 [DX4004]
MC68HC908QT1VP MC68HC908QT1VPE
MC68HC908QT2ACDW@SOIC8 [DX1032]
MC68HC908QT2ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2ACDWE@SOIC8 [DX1032]
MC68HC908QT2ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2ACFQ@DFN8 [DX4004]
MC68HC908QT2ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2ACFQE@DFN8 [DX4004]
MC68HC908QT2ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2ACP MC68HC908QT2ACP(a-trim)

MC68HC908QT2ACPE MC68HC908QT2ACPE(a-trim)
MC68HC908QT2AMDW@SOIC8 [DX1032]
MC68HC908QT2AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2AMDWE@SOIC8 [DX1032]
MC68HC908QT2AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2AMFQ@DFN8 [DX4004]
MC68HC908QT2AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2AMFQE@DFN8 [DX4004]
MC68HC908QT2AMFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2AMP MC68HC908QT2AMP(a-trim)
MC68HC908QT2AMPE MC68HC908QT2AMPE(a-trim)
MC68HC908QT2AVDW@SOIC8 [DX1032]
MC68HC908QT2AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2AVDWE@SOIC8 [DX1032]
MC68HC908QT2AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2AVFQ@DFN8 [DX4004]
MC68HC908QT2AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2AVFQE@DFN8 [DX4004]
MC68HC908QT2AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2AVP MC68HC908QT2AVP(a-trim)
MC68HC908QT2AVPE MC68HC908QT2AVPE(a-trim)
MC68HC908QT2CDW@SOIC8 [DX1032] MC68HC908QT2CDWE@SOIC8 [DX1032]
MC68HC908QT2CFQ@DFN8 [DX4004] MC68HC908QT2CFQE@DFN8 [DX4004]
MC68HC908QT2CP MC68HC908QT2CPE
MC68HC908QT2MDW@SOIC8 [DX1032] MC68HC908QT2MDWE@SOIC8 [DX1032]
MC68HC908QT2MFQ@DFN8 [DX4004] MC68HC908QT2MFQE@DFN8 [DX4004]
MC68HC908QT2MP MC68HC908QT2MPE
MC68HC908QT2VDW@SOIC8 [DX1032] MC68HC908QT2VDWE@SOIC8 [DX1032]
MC68HC908QT2VFQ@DFN8 [DX4004] MC68HC908QT2VFQE@DFN8 [DX4004]
MC68HC908QT2VP MC68HC908QT2VPE
MC68HC908QT4ACDW@SOIC8 [DX1032]
MC68HC908QT4ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4ACDWE@SOIC8 [DX1032]
MC68HC908QT4ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4ACFQ@DFN8 [DX4004]
MC68HC908QT4ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4ACFQE@DFN8 [DX4004]
MC68HC908QT4ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT4ACP MC68HC908QT4ACP(a-trim)
MC68HC908QT4ACPE MC68HC908QT4ACPE(a-trim)
MC68HC908QT4AMDW@SOIC8 [DX1032]
MC68HC908QT4AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4AMDWE@SOIC8 [DX1032]
MC68HC908QT4AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4AMFQ@DFN8 [DX4004]
MC68HC908QT4AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4AMFQE@DFN8 [DX4004]
MC68HC908QT4AMFQE@DFN8(a-trim) [DX4004]

MC68HC908QT4AMP MC68HC908QT4AMP(a-trim)
MC68HC908QT4AMPE MC68HC908QT4AMPE(a-trim)
MC68HC908QT4AVDW@SOIC8 [DX1032]
MC68HC908QT4AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4AVDWE@SOIC8 [DX1032]
MC68HC908QT4AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4AVFQ@DFN8 [DX4004]
MC68HC908QT4AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4AVFQE@DFN8 [DX4004]
MC68HC908QT4AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT4AVP MC68HC908QT4AVP(a-trim)
MC68HC908QT4AVPE MC68HC908QT4AVPE(a-trim)
MC68HC908QT4CDW@SOIC8 [DX1032] MC68HC908QT4CDWE@SOIC8 [DX1032]
MC68HC908QT4CFQ@DFN8 [DX4004] MC68HC908QT4CFQE@DFN8 [DX4004]
MC68HC908QT4CP MC68HC908QT4CPE
MC68HC908QT4MDW@SOIC8 [DX1032] MC68HC908QT4MDWE@SOIC8 [DX1032]
MC68HC908QT4MFQ@DFN8 [DX4004] MC68HC908QT4MFQE@DFN8 [DX4004]
MC68HC908QT4MP MC68HC908QT4MPE
MC68HC908QT4VDW@SOIC8 [DX1032] MC68HC908QT4VDWE@SOIC8 [DX1032]
MC68HC908QT4VFQ@DFN8 [DX4004] MC68HC908QT4VFQE@DFN8 [DX4004]
MC68HC908QT4VP MC68HC908QT4VPE
MC68HC908QY1ACDT@TSSOP16 [DX1001]
MC68HC908QY1ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1ACDTE@TSSOP16 [DX1001]
MC68HC908QY1ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1ACDW@SOIC16 [DX1072]
MC68HC908QY1ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1ACDWE@SOIC16 [DX1072]
MC68HC908QY1ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1ACP MC68HC908QY1ACP(a-trim)
MC68HC908QY1ACPE MC68HC908QY1ACPE(a-trim)
MC68HC908QY1AMDT@TSSOP16 [DX1001]
MC68HC908QY1AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1AMDTE@TSSOP16 [DX1001]
MC68HC908QY1AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1AMDW@SOIC16 [DX1072]
MC68HC908QY1AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1AMDWE@SOIC16 [DX1072]
MC68HC908QY1AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1AMP MC68HC908QY1AMP(a-trim)
MC68HC908QY1AMPE MC68HC908QY1AMPE(a-trim)
MC68HC908QY1AVDT@TSSOP16 [DX1001]
MC68HC908QY1AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1AVDTE@TSSOP16 [DX1001]
MC68HC908QY1AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1AVDW@SOIC16 [DX1072]
MC68HC908QY1AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1AVDWE@SOIC16 [DX1072]

MC68HC908QY1AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1AVP MC68HC908QY1AVP(a-trim)
MC68HC908QY1AVPE MC68HC908QY1AVPE(a-trim)
MC68HC908QY1CDT@TSSOP16 [DX1001]
MC68HC908QY1CDTE@TSSOP16 [DX1001]
MC68HC908QY1CDW@SOIC16 [DX1072] MC68HC908QY1CDWE@SOIC16 [DX1072]
MC68HC908QY1CP MC68HC908QY1CPE
MC68HC908QY1MDT@TSSOP16 [DX1001]
MC68HC908QY1MDTE@TSSOP16 [DX1001]
MC68HC908QY1MDW@SOIC16 [DX1072] MC68HC908QY1MDWE@SOIC16 [DX1072]
MC68HC908QY1MP MC68HC908QY1MPE
MC68HC908QY1VDT@TSSOP16 [DX1001]
MC68HC908QY1VDTE@TSSOP16 [DX1001]
MC68HC908QY1VDW@SOIC16 [DX1072] MC68HC908QY1VDWE@SOIC16 [DX1072]
MC68HC908QY1VP MC68HC908QY1VPE
MC68HC908QY2ACDT@TSSOP16 [DX1001]
MC68HC908QY2ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2ACDTE@TSSOP16 [DX1001]
MC68HC908QY2ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2ACDW@SOIC16 [DX1072]
MC68HC908QY2ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2ACDWE@SOIC16 [DX1072]
MC68HC908QY2ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2ACP MC68HC908QY2ACP(a-trim)
MC68HC908QY2ACPE MC68HC908QY2ACPE(a-trim)
MC68HC908QY2AMDT@TSSOP16 [DX1001]
MC68HC908QY2AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2AMDTE@TSSOP16 [DX1001]
MC68HC908QY2AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2AMDW@SOIC16 [DX1072]
MC68HC908QY2AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2AMDWE@SOIC16 [DX1072]
MC68HC908QY2AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2AMP MC68HC908QY2AMP(a-trim)
MC68HC908QY2AMPE MC68HC908QY2AMPE(a-trim)
MC68HC908QY2AVDT@TSSOP16 [DX1001]
MC68HC908QY2AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2AVDTE@TSSOP16 [DX1001]
MC68HC908QY2AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2AVDW@SOIC16 [DX1072]
MC68HC908QY2AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2AVDWE@SOIC16 [DX1072]
MC68HC908QY2AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2AVP MC68HC908QY2AVP(a-trim)
MC68HC908QY2AVPE MC68HC908QY2AVPE(a-trim)
MC68HC908QY2CDT@TSSOP16 [DX1001]
MC68HC908QY2CDTE@TSSOP16 [DX1001]
MC68HC908QY2CDW@SOIC16 [DX1072] MC68HC908QY2CDWE@SOIC16 [DX1072]

MC68HC908QY2CP MC68HC908QY2CPE
MC68HC908QY2MDT@TSSOP16 [DX1001]
MC68HC908QY2MDTE@TSSOP16 [DX1001]
MC68HC908QY2MDW@SOIC16 [DX1072] MC68HC908QY2MDWE@SOIC16 [DX1072]
MC68HC908QY2MP MC68HC908QY2MPE
MC68HC908QY2VDT@TSSOP16 [DX1001]
MC68HC908QY2VDTE@TSSOP16 [DX1001]
MC68HC908QY2VDW@SOIC16 [DX1072] MC68HC908QY2VDWE@SOIC16 [DX1072]
MC68HC908QY2VP MC68HC908QY2VPE
MC68HC908QY4ACDT@TSSOP16 [DX1001]
MC68HC908QY4ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4ACDTE@TSSOP16 [DX1001]
MC68HC908QY4ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4ACDW@SOIC16 [DX1072]
MC68HC908QY4ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4ACDWE@SOIC16 [DX1072]
MC68HC908QY4ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4ACP MC68HC908QY4ACP(a-trim)
MC68HC908QY4ACPE MC68HC908QY4ACPE(a-trim)
MC68HC908QY4AMDT@TSSOP16 [DX1001]
MC68HC908QY4AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4AMDTE@TSSOP16 [DX1001]
MC68HC908QY4AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4AMDW@SOIC16 [DX1072]
MC68HC908QY4AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4AMDWE@SOIC16 [DX1072]
MC68HC908QY4AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4AMP MC68HC908QY4AMP(a-trim)
MC68HC908QY4AMPE MC68HC908QY4AMPE(a-trim)
MC68HC908QY4AVDT@TSSOP16 [DX1001]
MC68HC908QY4AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4AVDTE@TSSOP16 [DX1001]
MC68HC908QY4AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4AVDW@SOIC16 [DX1072]
MC68HC908QY4AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4AVDWE@SOIC16 [DX1072]
MC68HC908QY4AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4AVP MC68HC908QY4AVP(a-trim)
MC68HC908QY4AVPE MC68HC908QY4AVPE(a-trim)
MC68HC908QY4CDT@TSSOP16 [DX1001]
MC68HC908QY4CDTE@TSSOP16 [DX1001]
MC68HC908QY4CDW@SOIC16 [DX1072] MC68HC908QY4CDWE@SOIC16 [DX1072]
MC68HC908QY4CP MC68HC908QY4CPE
MC68HC908QY4MDT@TSSOP16 [DX1001]
MC68HC908QY4MDTE@TSSOP16 [DX1001]
MC68HC908QY4MDW@SOIC16 [DX1072] MC68HC908QY4MDWE@SOIC16 [DX1072]
MC68HC908QY4MP MC68HC908QY4MPE
MC68HC908QY4VDT@TSSOP16 [DX1001]

MC68HC908QY4VDTE@TSSOP16 [DX1001]
MC68HC908QY4VDW@SOIC16 [DX1072]
MC68HC908QY4VDWE@SOIC16 [DX1072]
MC68HC908QY4VP
MC68HC908QY4VPE
MC68HC908QY8CDT@TSSOP16 [DX1001]
MC68HC908QY8CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8CDTE@TSSOP16 [DX1001]
MC68HC908QY8CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8CDW@SOIC16 [DX1072]
MC68HC908QY8CDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8CDWE@SOIC16 [DX1072]
MC68HC908QY8CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8CP
MC68HC908QY8CP(a-trim)
MC68HC908QY8CPE
MC68HC908QY8CPE(a-trim)
MC68HC908QY8MDT@TSSOP16 [DX1001]
MC68HC908QY8MDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8MDTE@TSSOP16 [DX1001]
MC68HC908QY8MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8MDW@SOIC16 [DX1072]
MC68HC908QY8MDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8MDWE@SOIC16 [DX1072]
MC68HC908QY8MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8MP
MC68HC908QY8MP(a-trim)
MC68HC908QY8MPE
MC68HC908QY8MPE(a-trim)
MC68HC908QY8VDT@TSSOP16 [DX1001]
MC68HC908QY8VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8VDTE@TSSOP16 [DX1001]
MC68HC908QY8VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8VDW@SOIC16 [DX1072]
MC68HC908QY8VDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8VDWE@SOIC16 [DX1072]
MC68HC908QY8VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8VP
MC68HC908QY8VP(a-trim)
MC68HC908QY8VPE
MC68HC908QY8VPE(a-trim)
MC68HC908SR12CB@SDIP42 [DX0042]
MC68HC908SR12CBE@SDIP42 [DX0042]
MC68HC908SR12CFA@TQFP48 [DX3007]
MC68HC908SR12CFAE@TQFP48 [DX3007]
MC68HC908SR12MB@SDIP42 [DX0042]
MC68HC908SR12MBE@SDIP42 [DX0042]
MC68HC908SR12MFA@TQFP48 [DX3007]
MC68HC908SR12MFAE@TQFP48 [DX3007]
MC68HC908SR12VB@SDIP42 [DX0042]
MC68HC908SR12VBE@SDIP42 [DX0042]
MC68HC908SR12VFA@TQFP48 [DX3007]
MC68HC908SR12VFAE@TQFP48 [DX3007]
MC68HCP11A0 [DX0001]
MC68HCP11A0@PLCC52 [DX2052]
MC68HCP11A1 [DX0001]
MC68HCP11A1@PLCC52 [DX2052]
MC68HCP11A8 [DX0001]
MC68HCP11A8@PLCC52 [DX2052]
MC68HCP11E1@PLCC52 [DX2052]
MC68HCP11E1@QFP52 [DX3010]
MC68HCP11E1CFN2 [DX2052]
MC68HCP11E1CFN3 [DX2052]
MC68HCP11E1CFU2 [DX3044]
MC68HCP11E1CFU3 [DX3044]

MC68HCP11E1MFN2 [DX2052]
MC68HCP11E1MFU2 [DX3044]
MC68HCP11E1VFN2 [DX2052]
MC68HCP11E1VFU2 [DX3044]
MC68HLC705J1ACDW [DX1033]
MC68HLC705J1ACP [DX0001]
MC68HLC705J1ACS [DX1001]
MC68HLC705J1ADW [DX1033]
MC68HLC705J1AP [DX0001]
MC68HLC705J1AS [DX1001]
MC68HLC705KJ1CDW [DX1033]
MC68HLC705KJ1CP [DX0001]
MC68HLC705KJ1CS [DX1001]
MC68HLC705KJ1DW [DX1033]
MC68HLC705KJ1P [DX0001]
MC68HLC705KJ1S [DX1001]
MC68HLC908JK1EIDW@SOIC20 [DX1033]
MC68HLC908JK1EIDWE@SOIC20 [DX1033]
MC68HLC908JK1EIP
MC68HLC908JK1EIPE
MC68HLC908JK3EIDW@SOIC20 [DX1033]
MC68HLC908JK3EIDWE@SOIC20 [DX1033]
MC68HLC908JK3EIP
MC68HLC908JK3EIPE
MC68HLC908JL3EIDW@SOIC28 [DX1033]
MC68HLC908JL3EIDWE@SOIC28 [DX1033]
MC68HLC908JL3EIFA@TQFP48 [DX3007]
MC68HLC908JL3EIFAE@TQFP48 [DX3007]
MC68HLC908JL3EIP
MC68HLC908JL3EIPE
MC68HRC705J1ACDW [DX1033]
MC68HRC705J1ACP [DX0001]
MC68HRC705J1ACS [DX1001]
MC68HRC705J1ADW [DX1033]
MC68HRC705J1AP [DX0001]
MC68HRC705J1AS [DX1001]
MC68HRC705KJ1CDW [DX1033]
MC68HRC705KJ1CP [DX0001]
MC68HRC705KJ1CS [DX1001]
MC68HRC705KJ1DW [DX1033]
MC68HRC705KJ1P [DX0001]
MC68HRC705KJ1S [DX1001]
MC68HRC908JK1CDW@SOIC20 [DX1033]
MC68HRC908JK1CDWE@SOIC20 [DX1033]
MC68HRC908JK1CP
MC68HRC908JK1CPE
MC68HRC908JK1ECDW@SOIC20 [DX1033]
MC68HRC908JK1ECDWE@SOIC20 [DX1033]
MC68HRC908JK1ECP
MC68HRC908JK1ECPE
MC68HRC908JK1EMDW@SOIC20 [DX1033]
MC68HRC908JK1EMDWE@SOIC20 [DX1033]
MC68HRC908JK1EMP
MC68HRC908JK1EMPE
MC68HRC908JK1EVDW@SOIC20 [DX1033]
MC68HRC908JK1EVDWE@SOIC20 [DX1033]
MC68HRC908JK1EVP
MC68HRC908JK1EVPE
MC68HRC908JK1MDW@SOIC20 [DX1033]
MC68HRC908JK1MDWE@SOIC20 [DX1033]
MC68HRC908JK1MP
MC68HRC908JK1MPE
MC68HRC908JK1VDW@SOIC20 [DX1033]
MC68HRC908JK1VDWE@SOIC20 [DX1033]
MC68HRC908JK1VP
MC68HRC908JK1VPE
MC68HRC908JK3CDW@SOIC20 [DX1033]
MC68HRC908JK3CDWE@SOIC20 [DX1033]
MC68HRC908JK3CP
MC68HRC908JK3CPE
MC68HRC908JK3ECDW@SOIC20 [DX1033]
MC68HRC908JK3ECDWE@SOIC20 [DX1033]

MC68HRC908JK3ECP
MC68HRC908JK3ECPE
MC68HRC908JK3EMDW@SOIC20 [DX1033]
MC68HRC908JK3EMDWE@SOIC20 [DX1033]
MC68HRC908JK3EMP
MC68HRC908JK3EMPE
MC68HRC908JK3EVDW@SOIC20 [DX1033]
MC68HRC908JK3EVDWE@SOIC20 [DX1033]
MC68HRC908JK3EVP
MC68HRC908JK3EVPE
MC68HRC908JK3MDW@SOIC20 [DX1033]
MC68HRC908JK3MDWE@SOIC20 [DX1033]
MC68HRC908JK3MP
MC68HRC908JK3MPE
MC68HRC908JK3VDW@SOIC20 [DX1033]
MC68HRC908JK3VDWE@SOIC20 [DX1033]
MC68HRC908JK3VP
MC68HRC908JK3VPE
MC68HRC908JL3CDW@SOIC28 [DX1033]
MC68HRC908JL3CDWE@SOIC28 [DX1033]
MC68HRC908JL3CP
MC68HRC908JL3CPE
MC68HRC908JL3ECDW@SOIC28 [DX1033]
MC68HRC908JL3ECDWE@SOIC28 [DX1033]
MC68HRC908JL3ECFA@TQFP48 [DX3007]
MC68HRC908JL3ECFAE@TQFP48 [DX3007]
MC68HRC908JL3ECP
MC68HRC908JL3ECPE
MC68HRC908JL3EMDW@SOIC28 [DX1033]
MC68HRC908JL3EMDWE@SOIC28 [DX1033]
MC68HRC908JL3EMFA@TQFP48 [DX3007]
MC68HRC908JL3EMFAE@TQFP48 [DX3007]
MC68HRC908JL3EMP
MC68HRC908JL3EMPE
MC68HRC908JL3EVDW@SOIC28 [DX1033]
MC68HRC908JL3EVDWE@SOIC28 [DX1033]
MC68HRC908JL3EVFA@TQFP48 [DX3007]
MC68HRC908JL3EVFAE@TQFP48 [DX3007]
MC68HRC908JL3EVP
MC68HRC908JL3EVPE
MC68HRC908JL3MDW@SOIC28 [DX1033]
MC68HRC908JL3MDWE@SOIC28 [DX1033]
MC68HRC908JL3MP
MC68HRC908JL3MPE
MC68HRC908JL3VDW@SOIC28 [DX1033]
MC68HRC908JL3VDWE@SOIC28 [DX1033]
MC68HRC908JL3VP
MC68HRC908JL3VPE
MC68HSC705C8A [DX0001]
MC68HSC705C8A@PLCC44 [DX2044]
MC68HSC705C8A@SDIP42 [DX0042]
MC68HSC705C8A@TQFP44 [DX3002]
MC68HSC705J1ACDW [DX1033]
MC68HSC705J1ACP [DX0001]
MC68HSC705J1ACS [DX1001]
MC68HSC705J1ADW [DX1033]
MC68HSC705J1AP [DX0001]
MC68HSC705J1AS [DX1001]
MC68HSC705KJ1CDW [DX1033]
MC68HSC705KJ1CP [DX0001]
MC68HSC705KJ1CS [DX1001]
MC68HSC705KJ1DW [DX1033]
MC68HSC705KJ1P [DX0001]
MC68HSC705KJ1S [DX1001]
MC68HSR705J1ACDW [DX1033]
MC68HSR705J1ACP [DX0001]
MC68HSR705J1ACS [DX1001]
MC68HSR705J1ADW [DX1033]
MC68HSR705J1AP [DX0001]
MC68HSR705J1AS [DX1001]

MC68HSR705KJ1CDW [DX1033]
MC68HSR705KJ1CP [DX0001]
MC68HSR705KJ1CS [DX1001]
MC68HSR705KJ1DW [DX1033]
MC68HSR705KJ1P [DX0001]
MC68HSR705KJ1S [DX1001]
MC68S711E9@PLCC52 [DX2052]
MC68S711E9FN@PLCC52 [DX2052]
MC912B32ACFU8@TQFP80 [DX3018]
MC912B32AMFU8@TQFP80 [DX3018]
MC912B32AVFU8@TQFP80 [DX3018]
MC912BC32ACFU8@TQFP80 [DX3018]
MC912BC32AMFU8@TQFP80 [DX3018]
MC912BC32AVFU8@TQFP80 [DX3018]
MC912D60ACFU8@TQFP80 [DX3018]
MC912D60ACPV8@TQFP112 [DX3026]
MC912D60AMFU8@TQFP80 [DX3018]
MC912D60AMPV8@TQFP112 [DX3026]
MC912D60AVFU8@TQFP80 [DX3018]
MC912D60AVPV8@TQFP112 [DX3026]
MC912D60CCFU8@TQFP80 [DX3018]
MC912D60CCPV8@TQFP112 [DX3026]
MC912D60CMFU8@TQFP80 [DX3018]
MC912D60CMPV8@TQFP112 [DX3026]
MC912D60CVFU8@TQFP80 [DX3018]
MC912D60CVPV8@TQFP112 [DX3026]
MC912D60PCFU8@TQFP80 [DX3018]
MC912D60PCPV8@TQFP112 [DX3026]
MC912D60PMFU8@TQFP80 [DX3018]
MC912D60PMPV8@TQFP112 [DX3026]
MC912D60PVFU8@TQFP80 [DX3018]
MC912D60PVPV8@TQFP112 [DX3026]
MC912DG128ACPV@TQFP112 [DX3026]
MC912DG128AMPV@TQFP112 [DX3026]
MC912DG128AVPV@TQFP112 [DX3026]
MC912DG128CCPV@TQFP112 [DX3026]
MC912DG128CMPV@TQFP112 [DX3026]
MC912DG128CVPV@TQFP112 [DX3026]
MC912DG128PCPV@TQFP112 [DX3026]
MC912DG128PMPV@TQFP112 [DX3026]
MC912DG128PVPV@TQFP112 [DX3026]
MC912DT128ACPV@TQFP112 [DX3026]
MC912DT128AMPV@TQFP112 [DX3026]
MC912DT128AVPV@TQFP112 [DX3026]
MC912DT128CCPV@TQFP112 [DX3026]
MC912DT128CMPV@TQFP112 [DX3026]
MC912DT128CVPV@TQFP112 [DX3026]
MC912DT128PCPV@TQFP112 [DX3026]
MC912DT128PMPV@TQFP112 [DX3026]
MC912DT128PVPV@TQFP112 [DX3026]
MC9RS08KA1CDB@DFN6 [DX4000]
MC9RS08KA1CDB@DFN6(auto trim) [DX4000]
MC9RS08KA1CDBE@DFN6 [DX4000]
MC9RS08KA1CDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1CPC
MC9RS08KA1CPC(auto trim)
MC9RS08KA1CPCE
MC9RS08KA1CPCE(auto trim)
MC9RS08KA1CSC@SOIC8 [DX1030]
MC9RS08KA1CSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1CSCE@SOIC8 [DX1030]
MC9RS08KA1CSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA1MDB@DFN6 [DX4000]
MC9RS08KA1MDB@DFN6(auto trim) [DX4000]
MC9RS08KA1MDBE@DFN6 [DX4000]
MC9RS08KA1MDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1MPC
MC9RS08KA1MPC(auto trim)
MC9RS08KA1MPCE
MC9RS08KA1MPCE(auto trim)
MC9RS08KA1MSC@SOIC8 [DX1030]
MC9RS08KA1MSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1MSCE@SOIC8 [DX1030]
MC9RS08KA1MSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA1VDB@DFN6 [DX4000]
MC9RS08KA1VDB@DFN6(auto trim) [DX4000]
MC9RS08KA1VDBE@DFN6 [DX4000]

MC9RS08KA1VDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1VPC MC9RS08KA1VPC(auto trim)
MC9RS08KA1VPCE MC9RS08KA1VPCE(auto trim)
MC9RS08KA1VSC@SOIC8 [DX1030]
MC9RS08KA1VSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1VSCE@SOIC8 [DX1030]
MC9RS08KA1VSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2CDB@DFN6 [DX4000]
MC9RS08KA2CDB@DFN6(auto trim) [DX4000]
MC9RS08KA2CDBE@DFN6 [DX4000]
MC9RS08KA2CDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2CPC MC9RS08KA2CPC(auto trim)
MC9RS08KA2CPCE MC9RS08KA2CPCE(auto trim)
MC9RS08KA2CSC@SOIC8 [DX1030]
MC9RS08KA2CSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2CSCE@SOIC8 [DX1030]
MC9RS08KA2CSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2MDB@DFN6 [DX4000]
MC9RS08KA2MDB@DFN6(auto trim) [DX4000]
MC9RS08KA2MDBE@DFN6 [DX4000]
MC9RS08KA2MDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2MPC MC9RS08KA2MPC(auto trim)
MC9RS08KA2MPCE MC9RS08KA2MPCE(auto trim)
MC9RS08KA2MSC@SOIC8 [DX1030]
MC9RS08KA2MSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2MSCE@SOIC8 [DX1030]
MC9RS08KA2MSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2VDB@DFN6 [DX4000]
MC9RS08KA2VDB@DFN6(auto trim) [DX4000]
MC9RS08KA2VDBE@DFN6 [DX4000]
MC9RS08KA2VDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2VPC MC9RS08KA2VPC(auto trim)
MC9RS08KA2VPCE MC9RS08KA2VPCE(auto trim)
MC9RS08KA2VSC@SOIC8 [DX1030]
MC9RS08KA2VSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2VSCE@SOIC8 [DX1030]
MC9RS08KA2VSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA4CPG MC9RS08KA4CPG(auto trim)
MC9RS08KA4CPGE MC9RS08KA4CPGE(auto trim)
MC9RS08KA4CPJ MC9RS08KA4CPJ(auto trim)
MC9RS08KA4CPJE MC9RS08KA4CPJE(auto trim)
MC9RS08KA4CTG@TSSOP16 [DX1001]
MC9RS08KA4CTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4CTGE@TSSOP16 [DX1001]
MC9RS08KA4CTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA4CWG@SOIC16 [DX1033]
MC9RS08KA4CWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4CWGE@SOIC16 [DX1033]

MC9RS08KA4CWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4CWJ@SOIC20 [DX1033]
MC9RS08KA4CWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4CWJE@SOIC20 [DX1033]
MC9RS08KA4CWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA4MPG MC9RS08KA4MPG(auto trim)
MC9RS08KA4MPGE MC9RS08KA4MPGE(auto trim)
MC9RS08KA4MPJ MC9RS08KA4MPJ(auto trim)
MC9RS08KA4MPJE MC9RS08KA4MPJE(auto trim)
MC9RS08KA4MTG@TSSOP16 [DX1001]
MC9RS08KA4MTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4MTGE@TSSOP16 [DX1001]
MC9RS08KA4MTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA4MWG@SOIC16 [DX1033]
MC9RS08KA4MWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4MWGE@SOIC16 [DX1033]
MC9RS08KA4MWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4MWJ@SOIC20 [DX1033]
MC9RS08KA4MWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4MWJE@SOIC20 [DX1033]
MC9RS08KA4MWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA4VPG MC9RS08KA4VPG(auto trim)
MC9RS08KA4VPGE MC9RS08KA4VPGE(auto trim)
MC9RS08KA4VPJ MC9RS08KA4VPJ(auto trim)
MC9RS08KA4VPJE MC9RS08KA4VPJE(auto trim)
MC9RS08KA4VTG@TSSOP16 [DX1001]
MC9RS08KA4VTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4VTGE@TSSOP16 [DX1001]
MC9RS08KA4VTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA4VWG@SOIC16 [DX1033]
MC9RS08KA4VWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4VWGE@SOIC16 [DX1033]
MC9RS08KA4VWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4VWJ@SOIC20 [DX1033]
MC9RS08KA4VWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4VWJE@SOIC20 [DX1033]
MC9RS08KA4VWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8CPG MC9RS08KA8CPG(auto trim)
MC9RS08KA8CPGE MC9RS08KA8CPGE(auto trim)
MC9RS08KA8CPJ MC9RS08KA8CPJ(auto trim)
MC9RS08KA8CPJE MC9RS08KA8CPJE(auto trim)
MC9RS08KA8CTG@TSSOP16 [DX1001]
MC9RS08KA8CTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8CTGE@TSSOP16 [DX1001]
MC9RS08KA8CTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA8CWG@SOIC16 [DX1033]
MC9RS08KA8CWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8CWGE@SOIC16 [DX1033]

MC9RS08KA8CWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8CWJ@SOIC20 [DX1033]
MC9RS08KA8CWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8CWJE@SOIC20 [DX1033]
MC9RS08KA8CWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8MPG MC9RS08KA8MPG(auto trim)
MC9RS08KA8MPGE MC9RS08KA8MPGE(auto trim)
MC9RS08KA8MPJ MC9RS08KA8MPJ(auto trim)
MC9RS08KA8MPJE MC9RS08KA8MPJE(auto trim)
MC9RS08KA8MTG@TSSOP16 [DX1001]
MC9RS08KA8MTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8MTGE@TSSOP16 [DX1001]
MC9RS08KA8MTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA8MWG@SOIC16 [DX1033]
MC9RS08KA8MWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8MWGE@SOIC16 [DX1033]
MC9RS08KA8MWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8MWJ@SOIC20 [DX1033]
MC9RS08KA8MWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8MWJE@SOIC20 [DX1033]
MC9RS08KA8MWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8VPG MC9RS08KA8VPG(auto trim)
MC9RS08KA8VPGE MC9RS08KA8VPGE(auto trim)
MC9RS08KA8VPJ MC9RS08KA8VPJ(auto trim)
MC9RS08KA8VPJE MC9RS08KA8VPJE(auto trim)
MC9RS08KA8VTG@TSSOP16 [DX1001]
MC9RS08KA8VTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8VTGE@TSSOP16 [DX1001]
MC9RS08KA8VTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA8VWG@SOIC16 [DX1033]
MC9RS08KA8VWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8VWGE@SOIC16 [DX1033]
MC9RS08KA8VWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8VWJ@SOIC20 [DX1033]
MC9RS08KA8VWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8VWJE@SOIC20 [DX1033]
MC9RS08KA8VWJE@SOIC20(auto trim) [DX1033]
MC9RS08KB12CDC@DFN8 [DX4004] MC9RS08KB12CSC@SOIC8 [DX1030]
MC9RS08KB12CSG@SOIC16 [DX1030] MC9RS08KB12CTG@TSSOP16 [DX1001]
MC9RS08KB12CWJ@SOIC20 [DX1033] MC9RS08KB12MDC@DFN8 [DX4004]
MC9RS08KB12MSC@SOIC8 [DX1030] MC9RS08KB12MSG@SOIC16 [DX1030]
MC9RS08KB12MTG@TSSOP16 [DX1001] MC9RS08KB12MWJ@SOIC20 [DX1033]
MC9RS08KB12VDC@DFN8 [DX4004] MC9RS08KB12VSC@SOIC8 [DX1030]
MC9RS08KB12VSG@SOIC16 [DX1030] MC9RS08KB12VTG@TSSOP16 [DX1001]
MC9RS08KB12VWJ@SOIC20 [DX1033] MC9RS08KB2CDC@DFN8 [DX4004]
MC9RS08KB2CSC@SOIC8 [DX1030] MC9RS08KB2CSG@SOIC16 [DX1030]
MC9RS08KB2CTG@TSSOP16 [DX1001] MC9RS08KB2CWJ@SOIC20 [DX1033]
MC9RS08KB2MDC@DFN8 [DX4004] MC9RS08KB2MSC@SOIC8 [DX1030]

MC9RS08KB2MSG@SOIC16 [DX1030]
MC9RS08KB2MTG@TSSOP16 [DX1001]
MC9RS08KB2MWJ@SOIC20 [DX1033]
MC9RS08KB2VDC@DFN8 [DX4004]
MC9RS08KB2VSC@SOIC8 [DX1030]
MC9RS08KB2VSG@SOIC16 [DX1030]
MC9RS08KB2VTG@TSSOP16 [DX1001]
MC9RS08KB2VWJ@SOIC20 [DX1033]
MC9RS08KB4CDC@DFN8 [DX4004]
MC9RS08KB4CSC@SOIC8 [DX1030]
MC9RS08KB4CSG@SOIC16 [DX1030]
MC9RS08KB4CTG@TSSOP16 [DX1001]
MC9RS08KB4CWJ@SOIC20 [DX1033]
MC9RS08KB4MDC@DFN8 [DX4004]
MC9RS08KB4MSC@SOIC8 [DX1030]
MC9RS08KB4MSG@SOIC16 [DX1030]
MC9RS08KB4MTG@TSSOP16 [DX1001]
MC9RS08KB4MWJ@SOIC20 [DX1033]
MC9RS08KB4VDC@DFN8 [DX4004]
MC9RS08KB4VSC@SOIC8 [DX1030]
MC9RS08KB4VSG@SOIC16 [DX1030]
MC9RS08KB4VTG@TSSOP16 [DX1001]
MC9RS08KB4VWJ@SOIC20 [DX1033]
MC9RS08KB8CDC@DFN8 [DX4004]
MC9RS08KB8CSC@SOIC8 [DX1030]
MC9RS08KB8CSG@SOIC16 [DX1030]
MC9RS08KB8CTG@TSSOP16 [DX1001]
MC9RS08KB8CWJ@SOIC20 [DX1033]
MC9RS08KB8MDC@DFN8 [DX4004]
MC9RS08KB8MSC@SOIC8 [DX1030]
MC9RS08KB8MSG@SOIC16 [DX1030]
MC9RS08KB8MTG@TSSOP16 [DX1001]
MC9RS08KB8MWJ@SOIC20 [DX1033]
MC9RS08KB8VDC@DFN8 [DX4004]
MC9RS08KB8VSC@SOIC8 [DX1030]
MC9RS08KB8VSG@SOIC16 [DX1030]
MC9RS08KB8VTG@TSSOP16 [DX1001]
MC9RS08KB8VWJ@SOIC20 [DX1033]
MC9RS08LA8CFT@QFN48 [DX4021]
MC9RS08LA8CFTE@QFN48 [DX4021]
MC9RS08LA8CLF@QFP48 [DX3007]
MC9RS08LA8CLFE@QFP48 [DX3007]
MC9RS08LA8MFT@QFN48 [DX4021]
MC9RS08LA8MFTE@QFN48 [DX4021]
MC9RS08LA8MLF@QFP48 [DX3007]
MC9RS08LA8MLFE@QFP48 [DX3007]
MC9RS08LA8VFT@QFN48 [DX4021]
MC9RS08LA8VFTE@QFN48 [DX4021]
MC9RS08LA8VLF@QFP48 [DX3007]
MC9RS08LA8VLFE@QFP48 [DX3007]
MC9RS08LE4CWL@SOIC28 [DX1033]
MC9RS08LE4CWLE@SOIC28 [DX1033]
MC9RS08LE4MWL@SOIC28 [DX1033]
MC9RS08LE4MWLE@SOIC28 [DX1033]
MC9RS08LE4VWL@SOIC28 [DX1033]
MC9RS08LE4VWLE@SOIC28 [DX1033]
MC9S08AC128CFG@QFP44 [DX3003]
MC9S08AC128CFGE@QFP44 [DX3003]
MC9S08AC128CFU@QFP64 [DX3014]
MC9S08AC128CFUE@QFP64 [DX3014]
MC9S08AC128CLK@QFP80 [DX3017]
MC9S08AC128CLKE@QFP80 [DX3017]
MC9S08AC128MFG@QFP44 [DX3003]
MC9S08AC128MFGE@QFP44 [DX3003]
MC9S08AC128MFU@QFP64 [DX3014]
MC9S08AC128MFUE@QFP64 [DX3014]
MC9S08AC128MLK@QFP80 [DX3017]
MC9S08AC128MLKE@QFP80 [DX3017]
MC9S08AC128VFG@QFP44 [DX3003]
MC9S08AC128VFGE@QFP44 [DX3003]
MC9S08AC128VFU@QFP64 [DX3014]
MC9S08AC128VFUE@QFP64 [DX3014]
MC9S08AC128VLK@QFP80 [DX3017]
MC9S08AC128VLKE@QFP80 [DX3017]
MC9S08AC16CFD@QFN48 [DX4021]
MC9S08AC16CFDE@QFN48 [DX4021]
MC9S08AC16CFG@LQFP44 [DX3003]
MC9S08AC16CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16CFGE@LQFP44 [DX3003]
MC9S08AC16CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC16CFJ@QFP32 [DX3001]
MC9S08AC16CFJE@QFP32 [DX3001]
MC9S08AC16MFD@QFN48 [DX4021]
MC9S08AC16MFDE@QFN48 [DX4021]
MC9S08AC16MFG@LQFP44 [DX3003]
MC9S08AC16MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16MFGE@LQFP44 [DX3003]
MC9S08AC16MFGE@LQFP44(*) [SA245A+B4404]

MC9S08AC16MFJ@QFP32 [DX3001]　　MC9S08AC16MFJE@QFP32 [DX3001]
MC9S08AC16VFD@QFN48 [DX4021]　　MC9S08AC16VFDE@QFN48 [DX4021]
MC9S08AC16VFG@LQFP44 [DX3003]
MC9S08AC16VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16VFGE@LQFP44 [DX3003]
MC9S08AC16VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC16VFJ@QFP32 [DX3001]　　MC9S08AC16VFJE@QFP32 [DX3001]
MC9S08AC32CFD@QFN48 [DX4021]　　MC9S08AC32CFDE@QFN48 [DX4021]
MC9S08AC32CFG@LQFP44 [DX3003]
MC9S08AC32CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32CFGE@LQFP44 [DX3003]
MC9S08AC32CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32CFJ@QFP32 [DX3001]　　MC9S08AC32CFJE@QFP32 [DX3001]
MC9S08AC32CFU@LQFP64 [DX3014]　　MC9S08AC32CFUE@LQFP64 [DX3014]
MC9S08AC32CPU@QFP64 [DX3011]　　MC9S08AC32CPUE@QFP64 [DX3011]
MC9S08AC32MFD@QFN48 [DX4021]　　MC9S08AC32MFDE@QFN48 [DX4021]
MC9S08AC32MFG@LQFP44 [DX3003]
MC9S08AC32MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32MFGE@LQFP44 [DX3003]
MC9S08AC32MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32MFJ@QFP32 [DX3001]　　MC9S08AC32MFJE@QFP32 [DX3001]
MC9S08AC32MFU@LQFP64 [DX3014]　　MC9S08AC32MFUE@LQFP64 [DX3014]
MC9S08AC32MPU@QFP64 [DX3011]　　MC9S08AC32MPUE@QFP64 [DX3011]
MC9S08AC32VFD@QFN48 [DX4021]　　MC9S08AC32VFDE@QFN48 [DX4021]
MC9S08AC32VFG@LQFP44 [DX3003]
MC9S08AC32VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32VFGE@LQFP44 [DX3003]
MC9S08AC32VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32VFJ@QFP32 [DX3001]　　MC9S08AC32VFJE@QFP32 [DX3001]
MC9S08AC32VFU@LQFP64 [DX3014]　　MC9S08AC32VFUE@LQFP64 [DX3014]
MC9S08AC32VPU@QFP64 [DX3011]　　MC9S08AC32VPUE@QFP64 [DX3011]
MC9S08AC48CFD@QFN48 [DX4021]　　MC9S08AC48CFDE@QFN48 [DX4021]
MC9S08AC48CFG@LQFP44 [DX3003]
MC9S08AC48CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48CFGE@LQFP44 [DX3003]
MC9S08AC48CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48CFJ@QFP32 [DX3001]　　MC9S08AC48CFJE@QFP32 [DX3001]
MC9S08AC48CFU@LQFP64 [DX3014]　　MC9S08AC48CFUE@LQFP64 [DX3014]
MC9S08AC48CPU@QFP64 [DX3011]　　MC9S08AC48CPUE@QFP64 [DX3011]
MC9S08AC48MFD@QFN48 [DX4021]　　MC9S08AC48MFDE@QFN48 [DX4021]
MC9S08AC48MFG@LQFP44 [DX3003]
MC9S08AC48MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48MFGE@LQFP44 [DX3003]
MC9S08AC48MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48MFJ@QFP32 [DX3001]　　MC9S08AC48MFJE@QFP32 [DX3001]
MC9S08AC48MFU@LQFP64 [DX3014]　　MC9S08AC48MFUE@LQFP64 [DX3014]
MC9S08AC48MPU@QFP64 [DX3011]　　MC9S08AC48MPUE@QFP64 [DX3011]
MC9S08AC48VFD@QFN48 [DX4021]　　MC9S08AC48VFDE@QFN48 [DX4021]

MC9S08AC48VFG@LQFP44 [DX3003]
MC9S08AC48VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48VFGE@LQFP44 [DX3003]
MC9S08AC48VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48VFJ@QFP32 [DX3001]
MC9S08AC48VFJE@QFP32 [DX3001]
MC9S08AC48VFU@LQFP64 [DX3014]
MC9S08AC48VFUE@LQFP64 [DX3014]
MC9S08AC48VPU@QFP64 [DX3011]
MC9S08AC48VPUE@QFP64 [DX3011]
MC9S08AC60CFD@QFN48 [DX4021]
MC9S08AC60CFDE@QFN48 [DX4021]
MC9S08AC60CFG@LQFP44 [DX3003]
MC9S08AC60CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60CFGE@LQFP44 [DX3003]
MC9S08AC60CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60CFJ@QFP32 [DX3001]
MC9S08AC60CFJE@QFP32 [DX3001]
MC9S08AC60CFU@LQFP64 [DX3014]
MC9S08AC60CFUE@LQFP64 [DX3014]
MC9S08AC60CPU@QFP64 [DX3011]
MC9S08AC60CPUE@QFP64 [DX3011]
MC9S08AC60MFD@QFN48 [DX4021]
MC9S08AC60MFDE@QFN48 [DX4021]
MC9S08AC60MFG@LQFP44 [DX3003]
MC9S08AC60MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60MFGE@LQFP44 [DX3003]
MC9S08AC60MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60MFJ@QFP32 [DX3001]
MC9S08AC60MFJE@QFP32 [DX3001]
MC9S08AC60MFU@LQFP64 [DX3014]
MC9S08AC60MFUE@LQFP64 [DX3014]
MC9S08AC60MPU@QFP64 [DX3011]
MC9S08AC60MPUE@QFP64 [DX3011]
MC9S08AC60VFD@QFN48 [DX4021]
MC9S08AC60VFDE@QFN48 [DX4021]
MC9S08AC60VFG@LQFP44 [DX3003]
MC9S08AC60VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60VFGE@LQFP44 [DX3003]
MC9S08AC60VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60VFJ@QFP32 [DX3001]
MC9S08AC60VFJE@QFP32 [DX3001]
MC9S08AC60VFU@LQFP64 [DX3014]
MC9S08AC60VFUE@LQFP64 [DX3014]
MC9S08AC60VPU@QFP64 [DX3011]
MC9S08AC60VPUE@QFP64 [DX3011]
MC9S08AC8CFD@QFN48 [DX4021]
MC9S08AC8CFDE@QFN48 [DX4021]
MC9S08AC8CFG@LQFP44 [DX3003]
MC9S08AC8CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8CFGE@LQFP44 [DX3003]
MC9S08AC8CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC8CFJ@QFP32 [DX3001]
MC9S08AC8CFJE@QFP32 [DX3001]
MC9S08AC8MFD@QFN48 [DX4021]
MC9S08AC8MFDE@QFN48 [DX4021]
MC9S08AC8MFG@LQFP44 [DX3003]
MC9S08AC8MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8MFGE@LQFP44 [DX3003]
MC9S08AC8MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC8MFJ@QFP32 [DX3001]
MC9S08AC8MFJE@QFP32 [DX3001]
MC9S08AC8VFD@QFN48 [DX4021]
MC9S08AC8VFDE@QFN48 [DX4021]
MC9S08AC8VFG@LQFP44 [DX3003]
MC9S08AC8VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8VFGE@LQFP44 [DX3003]
MC9S08AC8VFGE@LQFP44(*) [SA245A+B4404]

MC9S08AC8VFJ@QFP32 [DX3001]　　MC9S08AC8VFJE@QFP32 [DX3001]
MC9S08AC96CFG@QFP44 [DX3003]　　MC9S08AC96CFGE@QFP44 [DX3003]
MC9S08AC96CFU@QFP64 [DX3014]　　MC9S08AC96CFUE@QFP64 [DX3014]
MC9S08AC96CLK@QFP80 [DX3017]　　MC9S08AC96CLKE@QFP80 [DX3017]
MC9S08AC96MFG@QFP44 [DX3003]　　MC9S08AC96MFGE@QFP44 [DX3003]
MC9S08AC96MFU@QFP64 [DX3014]　　MC9S08AC96MFUE@QFP64 [DX3014]
MC9S08AC96MLK@QFP80 [DX3017]　　MC9S08AC96MLKE@QFP80 [DX3017]
MC9S08AC96VFG@QFP44 [DX3003]　　MC9S08AC96VFGE@QFP44 [DX3003]
MC9S08AC96VFU@QFP64 [DX3014]　　MC9S08AC96VFUE@QFP64 [DX3014]
MC9S08AC96VLK@QFP80 [DX3017]　　MC9S08AC96VLKE@QFP80 [DX3017]
MC9S08AW16CFD@QFN48 [DX4021]　　MC9S08AW16CFDE@QFN48 [DX4021]
MC9S08AW16CFG@LQFP44 [DX3003]
MC9S08AW16CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16CFGE@LQFP44 [DX3003]
MC9S08AW16CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16CFU@LQFP64 [DX3014]　　MC9S08AW16CFUE@LQFP64 [DX3014]
MC9S08AW16CPU@QFP64 [DX3011]　　MC9S08AW16CPUE@QFP64 [DX3011]
MC9S08AW16MFD@QFN48 [DX4021]　　MC9S08AW16MFDE@QFN48 [DX4021]
MC9S08AW16MFG@LQFP44 [DX3003]
MC9S08AW16MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16MFGE@LQFP44 [DX3003]
MC9S08AW16MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16MFU@LQFP64 [DX3014]　　MC9S08AW16MFUE@LQFP64 [DX3014]
MC9S08AW16MPU@QFP64 [DX3011]　　MC9S08AW16MPUE@QFP64 [DX3011]
MC9S08AW16VFD@QFN48 [DX4021]　　MC9S08AW16VFDE@QFN48 [DX4021]
MC9S08AW16VFG@LQFP44 [DX3003]
MC9S08AW16VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16VFGE@LQFP44 [DX3003]
MC9S08AW16VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16VFU@LQFP64 [DX3014]　　MC9S08AW16VFUE@LQFP64 [DX3014]
MC9S08AW16VPU@QFP64 [DX3011]　　MC9S08AW16VPUE@QFP64 [DX3011]
MC9S08AW32CFD@QFN48 [DX4021]　　MC9S08AW32CFDE@QFN48 [DX4021]
MC9S08AW32CFG@LQFP44 [DX3003]
MC9S08AW32CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW32CFGE@LQFP44 [DX3003]
MC9S08AW32CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32CFU@LQFP64 [DX3014]　　MC9S08AW32CFUE@LQFP64 [DX3014]
MC9S08AW32CPU@QFP64 [DX3011]　　MC9S08AW32CPUE@QFP64 [DX3011]
MC9S08AW32MFD@QFN48 [DX4021]　　MC9S08AW32MFDE@QFN48 [DX4021]
MC9S08AW32MFG@LQFP44 [DX3003]
MC9S08AW32MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW32MFGE@LQFP44 [DX3003]
MC9S08AW32MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32MFU@LQFP64 [DX3014]　　MC9S08AW32MFUE@LQFP64 [DX3014]
MC9S08AW32MPU@QFP64 [DX3011]　　MC9S08AW32MPUE@QFP64 [DX3011]
MC9S08AW32VFD@QFN48 [DX4021]　　MC9S08AW32VFDE@QFN48 [DX4021]
MC9S08AW32VFG@LQFP44 [DX3003]
MC9S08AW32VFG@LQFP44(*) [SA245A+B4404]

MC9S08AW32VFGE@LQFP44 [DX3003]
MC9S08AW32VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32VFU@LQFP64 [DX3014]　　MC9S08AW32VFUE@LQFP64 [DX3014]
MC9S08AW32VPU@QFP64 [DX3011]　　MC9S08AW32VPUE@QFP64 [DX3011]
MC9S08AW48CFD@QFN48 [DX4021]　　MC9S08AW48CFDE@QFN48 [DX4021]
MC9S08AW48CFG@LQFP44 [DX3003]
MC9S08AW48CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48CFGE@LQFP44 [DX3003]
MC9S08AW48CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48CFU@LQFP64 [DX3014]　　MC9S08AW48CFUE@LQFP64 [DX3014]
MC9S08AW48CPU@QFP64 [DX3011]　　MC9S08AW48CPUE@QFP64 [DX3011]
MC9S08AW48MFD@QFN48 [DX4021]　　MC9S08AW48MFDE@QFN48 [DX4021]
MC9S08AW48MFG@LQFP44 [DX3003]
MC9S08AW48MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48MFGE@LQFP44 [DX3003]
MC9S08AW48MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48MFU@LQFP64 [DX3014]　　MC9S08AW48MFUE@LQFP64 [DX3014]
MC9S08AW48MPU@QFP64 [DX3011]　　MC9S08AW48MPUE@QFP64 [DX3011]
MC9S08AW48VFD@QFN48 [DX4021]　　MC9S08AW48VFDE@QFN48 [DX4021]
MC9S08AW48VFG@LQFP44 [DX3003]
MC9S08AW48VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48VFGE@LQFP44 [DX3003]
MC9S08AW48VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48VFU@LQFP64 [DX3014]　　MC9S08AW48VFUE@LQFP64 [DX3014]
MC9S08AW48VPU@QFP64 [DX3011]　　MC9S08AW48VPUE@QFP64 [DX3011]
MC9S08AW60CFD@QFN48 [DX4021]　　MC9S08AW60CFDE@QFN48 [DX4021]
MC9S08AW60CFG@LQFP44 [DX3003]
MC9S08AW60CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60CFGE@LQFP44 [DX3003]
MC9S08AW60CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60CFU@LQFP64 [DX3014]　　MC9S08AW60CFUE@LQFP64 [DX3014]
MC9S08AW60CPU@QFP64 [DX3011]　　MC9S08AW60CPUE@QFP64 [DX3011]
MC9S08AW60MFD@QFN48 [DX4021]　　MC9S08AW60MFDE@QFN48 [DX4021]
MC9S08AW60MFG@LQFP44 [DX3003]
MC9S08AW60MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60MFGE@LQFP44 [DX3003]
MC9S08AW60MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60MFU@LQFP64 [DX3014]　　MC9S08AW60MFUE@LQFP64 [DX3014]
MC9S08AW60MPU@QFP64 [DX3011]　　MC9S08AW60MPUE@QFP64 [DX3011]
MC9S08AW60VFD@QFN48 [DX4021]　　MC9S08AW60VFDE@QFN48 [DX4021]
MC9S08AW60VFG@LQFP44 [DX3003]
MC9S08AW60VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60VFGE@LQFP44 [DX3003]
MC9S08AW60VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60VFU@LQFP64 [DX3014]　　MC9S08AW60VFUE@LQFP64 [DX3014]
MC9S08AW60VPU@QFP64 [DX3011]　　MC9S08AW60VPUE@QFP64 [DX3011]
MC9S08DN16CLC@QFP32 [DX3001]　　MC9S08DN16CLCE@QFP32 [DX3001]
MC9S08DN16CLF@QFP48 [DX3007]　　MC9S08DN16CLFE@QFP48 [DX3007]

MC9S08DN16CLH@QFP64 [DX3011]
MC9S08DN16CLHE@QFP64 [DX3011]
MC9S08DN16MLC@QFP32 [DX3001]
MC9S08DN16MLCE@QFP32 [DX3001]
MC9S08DN16MLF@QFP48 [DX3007]
MC9S08DN16MLFE@QFP48 [DX3007]
MC9S08DN16MLH@QFP64 [DX3011]
MC9S08DN16MLHE@QFP64 [DX3011]
MC9S08DN16VLC@QFP32 [DX3001]
MC9S08DN16VLCE@QFP32 [DX3001]
MC9S08DN16VLF@QFP48 [DX3007]
MC9S08DN16VLFE@QFP48 [DX3007]
MC9S08DN16VLH@QFP64 [DX3011]
MC9S08DN16VLHE@QFP64 [DX3011]
MC9S08DN32CLC@QFP32 [DX3001]
MC9S08DN32CLCE@QFP32 [DX3001]
MC9S08DN32CLF@QFP48 [DX3007]
MC9S08DN32CLFE@QFP48 [DX3007]
MC9S08DN32CLH@QFP64 [DX3011]
MC9S08DN32CLHE@QFP64 [DX3011]
MC9S08DN32MLC@QFP32 [DX3001]
MC9S08DN32MLCE@QFP32 [DX3001]
MC9S08DN32MLF@QFP48 [DX3007]
MC9S08DN32MLFE@QFP48 [DX3007]
MC9S08DN32MLH@QFP64 [DX3011]
MC9S08DN32MLHE@QFP64 [DX3011]
MC9S08DN32VLC@QFP32 [DX3001]
MC9S08DN32VLCE@QFP32 [DX3001]
MC9S08DN32VLF@QFP48 [DX3007]
MC9S08DN32VLFE@QFP48 [DX3007]
MC9S08DN32VLH@QFP64 [DX3011]
MC9S08DN32VLHE@QFP64 [DX3011]
MC9S08DN48CLC@QFP32 [DX3001]
MC9S08DN48CLCE@QFP32 [DX3001]
MC9S08DN48CLF@QFP48 [DX3007]
MC9S08DN48CLFE@QFP48 [DX3007]
MC9S08DN48CLH@QFP64 [DX3011]
MC9S08DN48CLHE@QFP64 [DX3011]
MC9S08DN48MLC@QFP32 [DX3001]
MC9S08DN48MLCE@QFP32 [DX3001]
MC9S08DN48MLF@QFP48 [DX3007]
MC9S08DN48MLFE@QFP48 [DX3007]
MC9S08DN48MLH@QFP64 [DX3011]
MC9S08DN48MLHE@QFP64 [DX3011]
MC9S08DN48VLC@QFP32 [DX3001]
MC9S08DN48VLCE@QFP32 [DX3001]
MC9S08DN48VLF@QFP48 [DX3007]
MC9S08DN48VLFE@QFP48 [DX3007]
MC9S08DN48VLH@QFP64 [DX3011]
MC9S08DN48VLHE@QFP64 [DX3011]
MC9S08DN60CLC@QFP32 [DX3001]
MC9S08DN60CLCE@QFP32 [DX3001]
MC9S08DN60CLF@QFP48 [DX3007]
MC9S08DN60CLFE@QFP48 [DX3007]
MC9S08DN60CLH@QFP64 [DX3011]
MC9S08DN60CLHE@QFP64 [DX3011]
MC9S08DN60MLC@QFP32 [DX3001]
MC9S08DN60MLCE@QFP32 [DX3001]
MC9S08DN60MLF@QFP48 [DX3007]
MC9S08DN60MLFE@QFP48 [DX3007]
MC9S08DN60MLH@QFP64 [DX3011]
MC9S08DN60MLHE@QFP64 [DX3011]
MC9S08DN60VLC@QFP32 [DX3001]
MC9S08DN60VLCE@QFP32 [DX3001]
MC9S08DN60VLF@QFP48 [DX3007]
MC9S08DN60VLFE@QFP48 [DX3007]
MC9S08DN60VLH@QFP64 [DX3011]
MC9S08DN60VLHE@QFP64 [DX3011]
MC9S08DV128CLF@QFP48 [DX3007]
MC9S08DV128CLFE@QFP48 [DX3007]
MC9S08DV128CLH@QFP64 [DX3011]
MC9S08DV128CLHE@QFP64 [DX3011]
MC9S08DV128CLL@QFP100 [DX3021]
MC9S08DV128CLLE@QFP100 [DX3021]
MC9S08DV128MLF@QFP48 [DX3007]
MC9S08DV128MLFE@QFP48 [DX3007]
MC9S08DV128MLH@QFP64 [DX3011]
MC9S08DV128MLHE@QFP64 [DX3011]
MC9S08DV128MLL@QFP100 [DX3021]
MC9S08DV128MLLE@QFP100 [DX3021]
MC9S08DV128VLF@QFP48 [DX3007]
MC9S08DV128VLFE@QFP48 [DX3007]
MC9S08DV128VLH@QFP64 [DX3011]
MC9S08DV128VLHE@QFP64 [DX3011]
MC9S08DV128VLL@QFP100 [DX3021]
MC9S08DV128VLLE@QFP100 [DX3021]
MC9S08DV16CLC@QFP32 [DX3001]
MC9S08DV16CLCE@QFP32 [DX3001]
MC9S08DV16CLF@QFP48 [DX3007]
MC9S08DV16CLFE@QFP48 [DX3007]
MC9S08DV16CLH@QFP64 [DX3011]
MC9S08DV16CLHE@QFP64 [DX3011]
MC9S08DV16MLC@QFP32 [DX3001]
MC9S08DV16MLCE@QFP32 [DX3001]
MC9S08DV16MLF@QFP48 [DX3007]
MC9S08DV16MLFE@QFP48 [DX3007]

MC9S08DV16MLH@QFP64 [DX3011]	MC9S08DV16MLHE@QFP64 [DX3011]
MC9S08DV16VLC@QFP32 [DX3001]	MC9S08DV16VLCE@QFP32 [DX3001]
MC9S08DV16VLF@QFP48 [DX3007]	MC9S08DV16VLFE@QFP48 [DX3007]
MC9S08DV16VLH@QFP64 [DX3011]	MC9S08DV16VLHE@QFP64 [DX3011]
MC9S08DV32CLC@QFP32 [DX3001]	MC9S08DV32CLCE@QFP32 [DX3001]
MC9S08DV32CLF@QFP48 [DX3007]	MC9S08DV32CLFE@QFP48 [DX3007]
MC9S08DV32CLH@QFP64 [DX3011]	MC9S08DV32CLHE@QFP64 [DX3011]
MC9S08DV32MLC@QFP32 [DX3001]	MC9S08DV32MLCE@QFP32 [DX3001]
MC9S08DV32MLF@QFP48 [DX3007]	MC9S08DV32MLFE@QFP48 [DX3007]
MC9S08DV32MLH@QFP64 [DX3011]	MC9S08DV32MLHE@QFP64 [DX3011]
MC9S08DV32VLC@QFP32 [DX3001]	MC9S08DV32VLCE@QFP32 [DX3001]
MC9S08DV32VLF@QFP48 [DX3007]	MC9S08DV32VLFE@QFP48 [DX3007]
MC9S08DV32VLH@QFP64 [DX3011]	MC9S08DV32VLHE@QFP64 [DX3011]
MC9S08DV48CLC@QFP32 [DX3001]	MC9S08DV48CLCE@QFP32 [DX3001]
MC9S08DV48CLF@QFP48 [DX3007]	MC9S08DV48CLFE@QFP48 [DX3007]
MC9S08DV48CLH@QFP64 [DX3011]	MC9S08DV48CLHE@QFP64 [DX3011]
MC9S08DV48MLC@QFP32 [DX3001]	MC9S08DV48MLCE@QFP32 [DX3001]
MC9S08DV48MLF@QFP48 [DX3007]	MC9S08DV48MLFE@QFP48 [DX3007]
MC9S08DV48MLH@QFP64 [DX3011]	MC9S08DV48MLHE@QFP64 [DX3011]
MC9S08DV48VLC@QFP32 [DX3001]	MC9S08DV48VLCE@QFP32 [DX3001]
MC9S08DV48VLF@QFP48 [DX3007]	MC9S08DV48VLFE@QFP48 [DX3007]
MC9S08DV48VLH@QFP64 [DX3011]	MC9S08DV48VLHE@QFP64 [DX3011]
MC9S08DV60CLC@QFP32 [DX3001]	MC9S08DV60CLCE@QFP32 [DX3001]
MC9S08DV60CLF@QFP48 [DX3007]	MC9S08DV60CLFE@QFP48 [DX3007]
MC9S08DV60CLH@QFP64 [DX3011]	MC9S08DV60CLHE@QFP64 [DX3011]
MC9S08DV60MLC@QFP32 [DX3001]	MC9S08DV60MLCE@QFP32 [DX3001]
MC9S08DV60MLF@QFP48 [DX3007]	MC9S08DV60MLFE@QFP48 [DX3007]
MC9S08DV60MLH@QFP64 [DX3011]	MC9S08DV60MLHE@QFP64 [DX3011]
MC9S08DV60VLC@QFP32 [DX3001]	MC9S08DV60VLCE@QFP32 [DX3001]
MC9S08DV60VLF@QFP48 [DX3007]	MC9S08DV60VLFE@QFP48 [DX3007]
MC9S08DV60VLH@QFP64 [DX3011]	MC9S08DV60VLHE@QFP64 [DX3011]
MC9S08DV96CLF@QFP48 [DX3007]	MC9S08DV96CLFE@QFP48 [DX3007]
MC9S08DV96CLH@QFP64 [DX3011]	MC9S08DV96CLHE@QFP64 [DX3011]
MC9S08DV96CLL@QFP100 [DX3021]	MC9S08DV96CLLE@QFP100 [DX3021]
MC9S08DV96MLF@QFP48 [DX3007]	MC9S08DV96MLFE@QFP48 [DX3007]
MC9S08DV96MLH@QFP64 [DX3011]	MC9S08DV96MLHE@QFP64 [DX3011]
MC9S08DV96MLL@QFP100 [DX3021]	MC9S08DV96MLLE@QFP100 [DX3021]
MC9S08DV96VLF@QFP48 [DX3007]	MC9S08DV96VLFE@QFP48 [DX3007]
MC9S08DV96VLH@QFP64 [DX3011]	MC9S08DV96VLHE@QFP64 [DX3011]
MC9S08DV96VLL@QFP100 [DX3021]	MC9S08DV96VLLE@QFP100 [DX3021]
MC9S08DZ128CLF@QFP48 [DX3007]	MC9S08DZ128CLFE@QFP48 [DX3007]
MC9S08DZ128CLH@QFP64 [DX3011]	MC9S08DZ128CLHE@QFP64 [DX3011]
MC9S08DZ128CLL@QFP100 [DX3021]	MC9S08DZ128CLLE@QFP100 [DX3021]
MC9S08DZ128MLF@QFP48 [DX3007]	MC9S08DZ128MLFE@QFP48 [DX3007]
MC9S08DZ128MLH@QFP64 [DX3011]	MC9S08DZ128MLHE@QFP64 [DX3011]
MC9S08DZ128MLL@QFP100 [DX3021]	MC9S08DZ128MLLE@QFP100 [DX3021]
MC9S08DZ128VLF@QFP48 [DX3007]	MC9S08DZ128VLFE@QFP48 [DX3007]
MC9S08DZ128VLH@QFP64 [DX3011]	MC9S08DZ128VLHE@QFP64 [DX3011]

MC9S08DZ128VLL@QFP100 [DX3021]	MC9S08DZ128VLLE@QFP100 [DX3021]
MC9S08DZ16CLC@QFP32 [DX3001]	MC9S08DZ16CLCE@QFP32 [DX3001]
MC9S08DZ16CLF@QFP48 [DX3007]	MC9S08DZ16CLFE@QFP48 [DX3007]
MC9S08DZ16CLH@QFP64 [DX3011]	MC9S08DZ16CLHE@QFP64 [DX3011]
MC9S08DZ16MLC@QFP32 [DX3001]	MC9S08DZ16MLCE@QFP32 [DX3001]
MC9S08DZ16MLF@QFP48 [DX3007]	MC9S08DZ16MLFE@QFP48 [DX3007]
MC9S08DZ16MLH@QFP64 [DX3011]	MC9S08DZ16MLHE@QFP64 [DX3011]
MC9S08DZ16VLC@QFP32 [DX3001]	MC9S08DZ16VLCE@QFP32 [DX3001]
MC9S08DZ16VLF@QFP48 [DX3007]	MC9S08DZ16VLFE@QFP48 [DX3007]
MC9S08DZ16VLH@QFP64 [DX3011]	MC9S08DZ16VLHE@QFP64 [DX3011]
MC9S08DZ32CLC@QFP32 [DX3001]	MC9S08DZ32CLCE@QFP32 [DX3001]
MC9S08DZ32CLF@QFP48 [DX3007]	MC9S08DZ32CLFE@QFP48 [DX3007]
MC9S08DZ32CLH@QFP64 [DX3011]	MC9S08DZ32CLHE@QFP64 [DX3011]
MC9S08DZ32MLC@QFP32 [DX3001]	MC9S08DZ32MLCE@QFP32 [DX3001]
MC9S08DZ32MLF@QFP48 [DX3007]	MC9S08DZ32MLFE@QFP48 [DX3007]
MC9S08DZ32MLH@QFP64 [DX3011]	MC9S08DZ32MLHE@QFP64 [DX3011]
MC9S08DZ32VLC@QFP32 [DX3001]	MC9S08DZ32VLCE@QFP32 [DX3001]
MC9S08DZ32VLF@QFP48 [DX3007]	MC9S08DZ32VLFE@QFP48 [DX3007]
MC9S08DZ32VLH@QFP64 [DX3011]	MC9S08DZ32VLHE@QFP64 [DX3011]
MC9S08DZ48CLC@QFP32 [DX3001]	MC9S08DZ48CLCE@QFP32 [DX3001]
MC9S08DZ48CLF@QFP48 [DX3007]	MC9S08DZ48CLFE@QFP48 [DX3007]
MC9S08DZ48CLH@QFP64 [DX3011]	MC9S08DZ48CLHE@QFP64 [DX3011]
MC9S08DZ48MLC@QFP32 [DX3001]	MC9S08DZ48MLCE@QFP32 [DX3001]
MC9S08DZ48MLF@QFP48 [DX3007]	MC9S08DZ48MLFE@QFP48 [DX3007]
MC9S08DZ48MLH@QFP64 [DX3011]	MC9S08DZ48MLHE@QFP64 [DX3011]
MC9S08DZ48VLC@QFP32 [DX3001]	MC9S08DZ48VLCE@QFP32 [DX3001]
MC9S08DZ48VLF@QFP48 [DX3007]	MC9S08DZ48VLFE@QFP48 [DX3007]
MC9S08DZ48VLH@QFP64 [DX3011]	MC9S08DZ48VLHE@QFP64 [DX3011]
MC9S08DZ60CLC@QFP32 [DX3001]	MC9S08DZ60CLCE@QFP32 [DX3001]
MC9S08DZ60CLF@QFP48 [DX3007]	MC9S08DZ60CLFE@QFP48 [DX3007]
MC9S08DZ60CLH@QFP64 [DX3011]	MC9S08DZ60CLHE@QFP64 [DX3011]
MC9S08DZ60MLC@QFP32 [DX3001]	MC9S08DZ60MLCE@QFP32 [DX3001]
MC9S08DZ60MLF@QFP48 [DX3007]	MC9S08DZ60MLFE@QFP48 [DX3007]
MC9S08DZ60MLH@QFP64 [DX3011]	MC9S08DZ60MLHE@QFP64 [DX3011]
MC9S08DZ60VLC@QFP32 [DX3001]	MC9S08DZ60VLCE@QFP32 [DX3001]
MC9S08DZ60VLF@QFP48 [DX3007]	MC9S08DZ60VLFE@QFP48 [DX3007]
MC9S08DZ60VLH@QFP64 [DX3011]	MC9S08DZ60VLHE@QFP64 [DX3011]
MC9S08DZ96CLF@QFP48 [DX3007]	MC9S08DZ96CLFE@QFP48 [DX3007]
MC9S08DZ96CLH@QFP64 [DX3011]	MC9S08DZ96CLHE@QFP64 [DX3011]
MC9S08DZ96CLL@QFP100 [DX3021]	MC9S08DZ96CLLE@QFP100 [DX3021]
MC9S08DZ96MLF@QFP48 [DX3007]	MC9S08DZ96MLFE@QFP48 [DX3007]
MC9S08DZ96MLH@QFP64 [DX3011]	MC9S08DZ96MLHE@QFP64 [DX3011]
MC9S08DZ96MLL@QFP100 [DX3021]	MC9S08DZ96MLLE@QFP100 [DX3021]
MC9S08DZ96VLF@QFP48 [DX3007]	MC9S08DZ96VLFE@QFP48 [DX3007]
MC9S08DZ96VLH@QFP64 [DX3011]	MC9S08DZ96VLHE@QFP64 [DX3011]
MC9S08DZ96VLL@QFP100 [DX3021]	MC9S08DZ96VLLE@QFP100 [DX3021]
MC9S08EL16CTJ@TSSOP20 [DX1000]	MC9S08EL16CTJE@TSSOP20 [DX1000]
MC9S08EL16CTL@TSSOP28 [DX1001]	MC9S08EL16CTLE@TSSOP28 [DX1001]

MC9S08EL16MTJ@TSSOP20 [DX1000]　　MC9S08EL16MTJE@TSSOP20 [DX1000]
MC9S08EL16MTL@TSSOP28 [DX1001]　　MC9S08EL16MTLE@TSSOP28 [DX1001]
MC9S08EL16VTJ@TSSOP20 [DX1000]　　MC9S08EL16VTJE@TSSOP20 [DX1000]
MC9S08EL16VTL@TSSOP28 [DX1001]　　MC9S08EL16VTLE@TSSOP28 [DX1001]
MC9S08EL32CTJ@TSSOP20 [DX1000]　　MC9S08EL32CTJE@TSSOP20 [DX1000]
MC9S08EL32CTL@TSSOP28 [DX1001]　　MC9S08EL32CTLE@TSSOP28 [DX1001]
MC9S08EL32MTJ@TSSOP20 [DX1000]　　MC9S08EL32MTJE@TSSOP20 [DX1000]
MC9S08EL32MTL@TSSOP28 [DX1001]　　MC9S08EL32MTLE@TSSOP28 [DX1001]
MC9S08EL32VTJ@TSSOP20 [DX1000]　　MC9S08EL32VTJE@TSSOP20 [DX1000]
MC9S08EL32VTL@TSSOP28 [DX1001]　　MC9S08EL32VTLE@TSSOP28 [DX1001]
MC9S08FL16CBM@SDIP32 [DX0032]
MC9S08FL16CBM@SDIP32(auto trim) [DX0032]
MC9S08FL16CLC@LQFP32 [DX3001]
MC9S08FL16CLC@LQFP32(auto trim) [DX3001]
MC9S08FL16MBM@SDIP32 [DX0032]
MC9S08FL16MBM@SDIP32(auto trim) [DX0032]
MC9S08FL16MLC@LQFP32 [DX3001]
MC9S08FL16MLC@LQFP32(auto trim) [DX3001]
MC9S08FL16VBM@SDIP32 [DX0032]
MC9S08FL16VBM@SDIP32(auto trim) [DX0032]
MC9S08FL16VLC@LQFP32 [DX3001]
MC9S08FL16VLC@LQFP32(auto trim) [DX3001]
MC9S08FL8CBM@SDIP32 [DX0032]
MC9S08FL8CBM@SDIP32(auto trim) [DX0032]
MC9S08FL8CLC@LQFP32 [DX3001]
MC9S08FL8CLC@LQFP32(auto trim) [DX3001]
MC9S08FL8MBM@SDIP32 [DX0032]
MC9S08FL8MBM@SDIP32(auto trim) [DX0032]
MC9S08FL8MLC@LQFP32 [DX3001]
MC9S08FL8MLC@LQFP32(auto trim) [DX3001]
MC9S08FL8VBM@SDIP32 [DX0032]
MC9S08FL8VBM@SDIP32(auto trim) [DX0032]
MC9S08FL8VLC@LQFP32 [DX3001]
MC9S08FL8VLC@LQFP32(auto trim) [DX3001]
MC9S08GB32ACFU@LQFP64 [DX3011]　　MC9S08GB32ACFUE@LQFP64 [DX3011]
MC9S08GB32AMFU@LQFP64 [DX3011]　　MC9S08GB32AMFUE@LQFP64 [DX3011]
MC9S08GB32AVFU@LQFP64 [DX3011]　　MC9S08GB32AVFUE@LQFP64 [DX3011]
MC9S08GB32CFU@LQFP64 [DX3011]　　MC9S08GB32CFUE@LQFP64 [DX3011]
MC9S08GB32MFU@LQFP64 [DX3011]　　MC9S08GB32MFUE@LQFP64 [DX3011]
MC9S08GB32VFU@LQFP64 [DX3011]　　MC9S08GB32VFUE@LQFP64 [DX3011]
MC9S08GB60ACFU@LQFP64 [DX3011]　　MC9S08GB60ACFUE@LQFP64 [DX3011]
MC9S08GB60AMFU@LQFP64 [DX3011]　　MC9S08GB60AMFUE@LQFP64 [DX3011]
MC9S08GB60AVFU@LQFP64 [DX3011]　　MC9S08GB60AVFUE@LQFP64 [DX3011]
MC9S08GB60CFU@LQFP64 [DX3011]　　MC9S08GB60CFUE@LQFP64 [DX3011]
MC9S08GB60MFU@LQFP64 [DX3011]　　MC9S08GB60MFUE@LQFP64 [DX3011]
MC9S08GB60VFU@LQFP64 [DX3011]　　MC9S08GB60VFUE@LQFP64 [DX3011]
MC9S08GT16ACB@SDIP42 [DX0042]　　MC9S08GT16ACBE@SDIP42 [DX0042]
MC9S08GT16ACFB@LQFP44 [DX3002]　　MC9S08GT16ACFBE@LQFP44 [DX3002]

MC9S08GT16ACFC@MLF32 [DX4015]
MC9S08GT16ACFCE@MLF32 [DX4015]
MC9S08GT16ACFD@QFN48 [DX4021]
MC9S08GT16ACFDE@QFN48 [DX4021]
MC9S08GT16AMB@SDIP42 [DX0042]
MC9S08GT16AMBE@SDIP42 [DX0042]
MC9S08GT16AMFB@LQFP44 [DX3002]
MC9S08GT16AMFBE@LQFP44 [DX3002]
MC9S08GT16AMFC@MLF32 [DX4015]
MC9S08GT16AMFCE@MLF32 [DX4015]
MC9S08GT16AMFD@QFN48 [DX4021]
MC9S08GT16AMFDE@QFN48 [DX4021]
MC9S08GT16AVB@SDIP42 [DX0042]
MC9S08GT16AVBE@SDIP42 [DX0042]
MC9S08GT16AVFB@LQFP44 [DX3002]
MC9S08GT16AVFBE@LQFP44 [DX3002]
MC9S08GT16AVFC@MLF32 [DX4015]
MC9S08GT16AVFCE@MLF32 [DX4015]
MC9S08GT16AVFD@QFN48 [DX4021]
MC9S08GT16AVFDE@QFN48 [DX4021]
MC9S08GT16CB@SDIP42 [DX0042]
MC9S08GT16CBE@SDIP42 [DX0042]
MC9S08GT16CFB@LQFP44 [DX3002]
MC9S08GT16CFBE@LQFP44 [DX3002]
MC9S08GT16CFD@QFN48 [DX4021]
MC9S08GT16CFDE@QFN48 [DX4021]
MC9S08GT16MB@SDIP42 [DX0042]
MC9S08GT16MBE@SDIP42 [DX0042]
MC9S08GT16MFB@LQFP44 [DX3002]
MC9S08GT16MFBE@LQFP44 [DX3002]
MC9S08GT16MFD@QFN48 [DX4021]
MC9S08GT16MFDE@QFN48 [DX4021]
MC9S08GT16VB@SDIP42 [DX0042]
MC9S08GT16VBE@SDIP42 [DX0042]
MC9S08GT16VFB@LQFP44 [DX3002]
MC9S08GT16VFBE@LQFP44 [DX3002]
MC9S08GT16VFD@QFN48 [DX4021]
MC9S08GT16VFDE@QFN48 [DX4021]
MC9S08GT32ACB@SDIP42 [DX0042]
MC9S08GT32ACBE@SDIP42 [DX0042]
MC9S08GT32ACFB@LQFP44 [DX3002]
MC9S08GT32ACFBE@LQFP44 [DX3002]
MC9S08GT32ACFD@QFN48 [DX4021]
MC9S08GT32ACFDE@QFN48 [DX4021]
MC9S08GT32AMB@SDIP42 [DX0042]
MC9S08GT32AMBE@SDIP42 [DX0042]
MC9S08GT32AMFB@LQFP44 [DX3002]
MC9S08GT32AMFBE@LQFP44 [DX3002]
MC9S08GT32AMFD@QFN48 [DX4021]
MC9S08GT32AMFDE@QFN48 [DX4021]
MC9S08GT32AVB@SDIP42 [DX0042]
MC9S08GT32AVBE@SDIP42 [DX0042]
MC9S08GT32AVFB@LQFP44 [DX3002]
MC9S08GT32AVFBE@LQFP44 [DX3002]
MC9S08GT32AVFD@QFN48 [DX4021]
MC9S08GT32AVFDE@QFN48 [DX4021]
MC9S08GT32CB@SDIP42 [DX0042]
MC9S08GT32CBE@SDIP42 [DX0042]
MC9S08GT32CFB@LQFP44 [DX3002]
MC9S08GT32CFBE@LQFP44 [DX3002]
MC9S08GT32CFD@QFN48 [DX4021]
MC9S08GT32CFDE@QFN48 [DX4021]
MC9S08GT32MB@SDIP42 [DX0042]
MC9S08GT32MBE@SDIP42 [DX0042]
MC9S08GT32MFB@LQFP44 [DX3002]
MC9S08GT32MFBE@LQFP44 [DX3002]
MC9S08GT32MFD@QFN48 [DX4021]
MC9S08GT32MFDE@QFN48 [DX4021]
MC9S08GT32VB@SDIP42 [DX0042]
MC9S08GT32VBE@SDIP42 [DX0042]
MC9S08GT32VFB@LQFP44 [DX3002]
MC9S08GT32VFBE@LQFP44 [DX3002]
MC9S08GT32VFD@QFN48 [DX4021]
MC9S08GT32VFDE@QFN48 [DX4021]
MC9S08GT60ACB@SDIP42 [DX0042]
MC9S08GT60ACBE@SDIP42 [DX0042]
MC9S08GT60ACFB@LQFP44 [DX3002]
MC9S08GT60ACFBE@LQFP44 [DX3002]
MC9S08GT60ACFD@QFN48 [DX4021]
MC9S08GT60ACFDE@QFN48 [DX4021]
MC9S08GT60AMB@SDIP42 [DX0042]
MC9S08GT60AMBE@SDIP42 [DX0042]
MC9S08GT60AMFB@LQFP44 [DX3002]
MC9S08GT60AMFBE@LQFP44 [DX3002]
MC9S08GT60AMFD@QFN48 [DX4021]
MC9S08GT60AMFDE@QFN48 [DX4021]
MC9S08GT60AVB@SDIP42 [DX0042]
MC9S08GT60AVBE@SDIP42 [DX0042]
MC9S08GT60AVFB@LQFP44 [DX3002]
MC9S08GT60AVFBE@LQFP44 [DX3002]
MC9S08GT60AVFD@QFN48 [DX4021]
MC9S08GT60AVFDE@QFN48 [DX4021]
MC9S08GT60CB@SDIP42 [DX0042]
MC9S08GT60CBE@SDIP42 [DX0042]
MC9S08GT60CFB@LQFP44 [DX3002]
MC9S08GT60CFBE@LQFP44 [DX3002]

MC9S08GT60CFD@QFN48 [DX4021]
MC9S08GT60CFDE@QFN48 [DX4021]
MC9S08GT60MB@SDIP42 [DX0042]
MC9S08GT60MBE@SDIP42 [DX0042]
MC9S08GT60MFB@LQFP44 [DX3002]
MC9S08GT60MFBE@LQFP44 [DX3002]
MC9S08GT60MFD@QFN48 [DX4021]
MC9S08GT60MFDE@QFN48 [DX4021]
MC9S08GT60VB@SDIP42 [DX0042]
MC9S08GT60VBE@SDIP42 [DX0042]
MC9S08GT60VFB@LQFP44 [DX3002]
MC9S08GT60VFBE@LQFP44 [DX3002]
MC9S08GT60VFD@QFN48 [DX4021]
MC9S08GT60VFDE@QFN48 [DX4021]
MC9S08GT8ACB@SDIP42 [DX0042]
MC9S08GT8ACBE@SDIP42 [DX0042]
MC9S08GT8ACFB@LQFP44 [DX3002]
MC9S08GT8ACFBE@LQFP44 [DX3002]
MC9S08GT8ACFC@MLF32 [DX4015]
MC9S08GT8ACFCE@MLF32 [DX4015]
MC9S08GT8ACFD@QFN48 [DX4021]
MC9S08GT8ACFDE@QFN48 [DX4021]
MC9S08GT8AMB@SDIP42 [DX0042]
MC9S08GT8AMBE@SDIP42 [DX0042]
MC9S08GT8AMFB@LQFP44 [DX3002]
MC9S08GT8AMFBE@LQFP44 [DX3002]
MC9S08GT8AMFC@MLF32 [DX4015]
MC9S08GT8AMFCE@MLF32 [DX4015]
MC9S08GT8AMFD@QFN48 [DX4021]
MC9S08GT8AMFDE@QFN48 [DX4021]
MC9S08GT8AVB@SDIP42 [DX0042]
MC9S08GT8AVBE@SDIP42 [DX0042]
MC9S08GT8AVFB@LQFP44 [DX3002]
MC9S08GT8AVFBE@LQFP44 [DX3002]
MC9S08GT8AVFC@MLF32 [DX4015]
MC9S08GT8AVFCE@MLF32 [DX4015]
MC9S08GT8AVFD@QFN48 [DX4021]
MC9S08GT8AVFDE@QFN48 [DX4021]
MC9S08JE128CLH@QFP64 [DX3011]
MC9S08JE128CLK@QFP80 [DX3016]
MC9S08JE128MLH@QFP64 [DX3011]
MC9S08JE128MLK@QFP80 [DX3016]
MC9S08JE128VLH@QFP64 [DX3011]
MC9S08JE128VLK@QFP80 [DX3016]
MC9S08JE64CLH@QFP64 [DX3011]
MC9S08JE64MLH@QFP64 [DX3011]
MC9S08JE64VLH@QFP64 [DX3011]
MC9S08JM16CGT@QFN48 [DX4021]
MC9S08JM16CGTE@QFN48 [DX4021]
MC9S08JM16CLC@QFP32 [DX3001]
MC9S08JM16CLCE@QFP32 [DX3001]
MC9S08JM16CLD@QFP44 [DX3003]
MC9S08JM16CLDE@QFP44 [DX3003]
MC9S08JM16MGT@QFN48 [DX4021]
MC9S08JM16MGTE@QFN48 [DX4021]
MC9S08JM16MLC@QFP32 [DX3001]
MC9S08JM16MLCE@QFP32 [DX3001]
MC9S08JM16MLD@QFP44 [DX3003]
MC9S08JM16MLDE@QFP44 [DX3003]
MC9S08JM16VGT@QFN48 [DX4021]
MC9S08JM16VGTE@QFN48 [DX4021]
MC9S08JM16VLC@QFP32 [DX3001]
MC9S08JM16VLCE@QFP32 [DX3001]
MC9S08JM16VLD@QFP44 [DX3003]
MC9S08JM16VLDE@QFP44 [DX3003]
MC9S08JM32CGT@QFN48 [DX4021]
MC9S08JM32CGTE@QFN48 [DX4021]
MC9S08JM32CLD@QFP44 [DX3003]
MC9S08JM32CLDE@QFP44 [DX3003]
MC9S08JM32CLH@QFP64 [DX3011]
MC9S08JM32CLHE@QFP64 [DX3011]
MC9S08JM32CQH@QFP64 [DX3014]
MC9S08JM32CQHE@QFP64 [DX3014]
MC9S08JM32MGT@QFN48 [DX4021]
MC9S08JM32MGTE@QFN48 [DX4021]
MC9S08JM32MLD@QFP44 [DX3003]
MC9S08JM32MLDE@QFP44 [DX3003]
MC9S08JM32MLH@QFP64 [DX3011]
MC9S08JM32MLHE@QFP64 [DX3011]
MC9S08JM32MQH@QFP64 [DX3014]
MC9S08JM32MQHE@QFP64 [DX3014]
MC9S08JM32VGT@QFN48 [DX4021]
MC9S08JM32VGTE@QFN48 [DX4021]
MC9S08JM32VLD@QFP44 [DX3003]
MC9S08JM32VLDE@QFP44 [DX3003]
MC9S08JM32VLH@QFP64 [DX3011]
MC9S08JM32VLHE@QFP64 [DX3011]
MC9S08JM32VQH@QFP64 [DX3014]
MC9S08JM32VQHE@QFP64 [DX3014]
MC9S08JM60CGT@QFN48 [DX4021]
MC9S08JM60CGTE@QFN48 [DX4021]
MC9S08JM60CLD@QFP44 [DX3003]
MC9S08JM60CLDE@QFP44 [DX3003]
MC9S08JM60CLH@QFP64 [DX3011]
MC9S08JM60CLHE@QFP64 [DX3011]
MC9S08JM60CQH@QFP64 [DX3014]

MC9S08JM60CQHE@QFP64 [DX3014]
MC9S08JM60MGTE@QFN48 [DX4021]
MC9S08JM60MLDE@QFP44 [DX3003]
MC9S08JM60MLHE@QFP64 [DX3011]
MC9S08JM60MQHE@QFP64 [DX3014]
MC9S08JM60VGTE@QFN48 [DX4021]
MC9S08JM60VLDE@QFP44 [DX3003]
MC9S08JM60VLHE@QFP64 [DX3011]
MC9S08JM60VQHE@QFP64 [DX3014]
MC9S08JM8CGTE@QFN48 [DX4021]
MC9S08JM8CLCE@QFP32 [DX3001]
MC9S08JM8CLDE@QFP44 [DX3003]
MC9S08JM8MGTE@QFN48 [DX4021]
MC9S08JM8MLCE@QFP32 [DX3001]
MC9S08JM8MLDE@QFP44 [DX3003]
MC9S08JM8VGTE@QFN48 [DX4021]
MC9S08JM8VLCE@QFP32 [DX3001]
MC9S08JM8VLDE@QFP44 [DX3003]
MC9S08JS16CWJ@SOIC20 [DX1033]
MC9S08JS16LCWJ@SOIC20 [DX1033]
MC9S08JS16LMWJ@SOIC20 [DX1033]
MC9S08JS16LVWJ@SOIC20 [DX1033]
MC9S08JS16MWJ@SOIC20 [DX1033]
MC9S08JS16VWJ@SOIC20 [DX1033]
MC9S08JS8CWJ@SOIC20 [DX1033]
MC9S08JS8LCWJ@SOIC20 [DX1033]
MC9S08JS8LMWJ@SOIC20 [DX1033]
MC9S08JS8LVWJ@SOIC20 [DX1033]
MC9S08JS8MWJ@SOIC20 [DX1033]
MC9S08JS8VWJ@SOIC20 [DX1033]
MC9S08LC36LHE@QFP64 [DX3011]
MC9S08LC36LKE@QFP80 [DX3016]
MC9S08LC60LHE@QFP64 [DX3011]
MC9S08LC60LKE@QFP80 [DX3016]
MC9S08LG16CLF@QFP48(auto trim) [DX3007]
MC9S08LG16CLFE@QFP48 [DX3007]
MC9S08LG16CLFE@QFP48(auto trim) [DX3007]
MC9S08LG16CLH@QFP64 [DX3011]
MC9S08LG16CLH@QFP64(auto trim) [DX3011]
MC9S08LG16CLHE@QFP64 [DX3011]
MC9S08LG16CLHE@QFP64(auto trim) [DX3011]
MC9S08LG16MLF@QFP48 [DX3007]
MC9S08LG16MLF@QFP48(auto trim) [DX3007]
MC9S08LG16MLFE@QFP48 [DX3007]
MC9S08LG16MLFE@QFP48(auto trim) [DX3007]
MC9S08LG16MLH@QFP64 [DX3011]
MC9S08LG16MLH@QFP64(auto trim) [DX3011]
MC9S08LG16MLHE@QFP64 [DX3011]
MC9S08JM60MGT@QFN48 [DX4021]
MC9S08JM60MLD@QFP44 [DX3003]
MC9S08JM60MLH@QFP64 [DX3011]
MC9S08JM60MQH@QFP64 [DX3014]
MC9S08JM60VGT@QFN48 [DX4021]
MC9S08JM60VLD@QFP44 [DX3003]
MC9S08JM60VLH@QFP64 [DX3011]
MC9S08JM60VQH@QFP64 [DX3014]
MC9S08JM8CGT@QFN48 [DX4021]
MC9S08JM8CLC@QFP32 [DX3001]
MC9S08JM8CLD@QFP44 [DX3003]
MC9S08JM8MGT@QFN48 [DX4021]
MC9S08JM8MLC@QFP32 [DX3001]
MC9S08JM8MLD@QFP44 [DX3003]
MC9S08JM8VGT@QFN48 [DX4021]
MC9S08JM8VLC@QFP32 [DX3001]
MC9S08JM8VLD@QFP44 [DX3003]
MC9S08JS16CFK@QFN24 [DX4034]
MC9S08JS16LCFK@QFN24 [DX4034]
MC9S08JS16LMFK@QFN24 [DX4034]
MC9S08JS16LVFK@QFN24 [DX4034]
MC9S08JS16MFK@QFN24 [DX4034]
MC9S08JS16VFK@QFN24 [DX4034]
MC9S08JS8CFK@QFN24 [DX4034]
MC9S08JS8LCFK@QFN24 [DX4034]
MC9S08JS8LMFK@QFN24 [DX4034]
MC9S08JS8LVFK@QFN24 [DX4034]
MC9S08JS8MFK@QFN24 [DX4034]
MC9S08JS8VFK@QFN24 [DX4034]
MC9S08LC36LH@QFP64 [DX3011]
MC9S08LC36LK@QFP80 [DX3016]
MC9S08LC60LH@QFP64 [DX3011]
MC9S08LC60LK@QFP80 [DX3016]
MC9S08LG16CLF@QFP48 [DX3007]

MC9S08LG16MLHE@QFP64(auto trim) [DX3011]
MC9S08LG16VLF@QFP48 [DX3007]
MC9S08LG16VLF@QFP48(auto trim) [DX3007]
MC9S08LG16VLFE@QFP48 [DX3007]
MC9S08LG16VLFE@QFP48(auto trim) [DX3007]
MC9S08LG16VLH@QFP64 [DX3011]
MC9S08LG16VLH@QFP64(auto trim) [DX3011]
MC9S08LG16VLHE@QFP64 [DX3011]
MC9S08LG16VLHE@QFP64(auto trim) [DX3011]
MC9S08LG32CLF@QFP48 [DX3007]
MC9S08LG32CLF@QFP48(auto trim) [DX3007]
MC9S08LG32CLFE@QFP48 [DX3007]
MC9S08LG32CLFE@QFP48(auto trim) [DX3007]
MC9S08LG32CLH@QFP64 [DX3011]
MC9S08LG32CLH@QFP64(auto trim) [DX3011]
MC9S08LG32CLHE@QFP64 [DX3011]
MC9S08LG32CLHE@QFP64(auto trim) [DX3011]
MC9S08LG32CLK@QFP80 [DX3017]
MC9S08LG32CLK@QFP80(auto trim) [DX3017]
MC9S08LG32CLKE@QFP80 [DX3017]
MC9S08LG32CLKE@QFP80(auto trim) [DX3017]
MC9S08LG32MLF@QFP48 [DX3007]
MC9S08LG32MLF@QFP48(auto trim) [DX3007]
MC9S08LG32MLFE@QFP48 [DX3007]
MC9S08LG32MLFE@QFP48(auto trim) [DX3007]
MC9S08LG32MLH@QFP64 [DX3011]
MC9S08LG32MLH@QFP64(auto trim) [DX3011]
MC9S08LG32MLHE@QFP64 [DX3011]
MC9S08LG32MLHE@QFP64(auto trim) [DX3011]
MC9S08LG32MLK@QFP80 [DX3017]
MC9S08LG32MLK@QFP80(auto trim) [DX3017]
MC9S08LG32MLKE@QFP80 [DX3017]
MC9S08LG32MLKE@QFP80(auto trim) [DX3017]
MC9S08LG32VLF@QFP48 [DX3007]
MC9S08LG32VLF@QFP48(auto trim) [DX3007]
MC9S08LG32VLFE@QFP48 [DX3007]
MC9S08LG32VLFE@QFP48(auto trim) [DX3007]
MC9S08LG32VLH@QFP64 [DX3011]
MC9S08LG32VLH@QFP64(auto trim) [DX3011]
MC9S08LG32VLHE@QFP64 [DX3011]
MC9S08LG32VLHE@QFP64(auto trim) [DX3011]
MC9S08LG32VLK@QFP80 [DX3017]
MC9S08LG32VLK@QFP80(auto trim) [DX3017]
MC9S08LG32VLKE@QFP80 [DX3017]
MC9S08LG32VLKE@QFP80(auto trim) [DX3017]
MC9S08LL16CGT@QFN48 [DX4021]
MC9S08LL16CGT@QFN48(auto trim) [DX4021]
MC9S08LL16CLF@LQFP48 [DX3007]

MC9S08LL16CLF@LQFP48(auto trim) [DX3007]
MC9S08LL16CLH@LQFP64 [DX3011]
MC9S08LL16CLH@LQFP64(auto trim) [DX3011]
MC9S08LL16MGT@QFN48 [DX4021]
MC9S08LL16MGT@QFN48(auto trim) [DX4021]
MC9S08LL16MLF@LQFP48 [DX3007]
MC9S08LL16MLF@LQFP48(auto trim) [DX3007]
MC9S08LL16MLH@LQFP64 [DX3011]
MC9S08LL16MLH@LQFP64(auto trim) [DX3011]
MC9S08LL16VGT@QFN48 [DX4021]
MC9S08LL16VGT@QFN48(auto trim) [DX4021]
MC9S08LL16VLF@LQFP48 [DX3007]
MC9S08LL16VLF@LQFP48(auto trim) [DX3007]
MC9S08LL16VLH@LQFP64 [DX3011]
MC9S08LL16VLH@LQFP64(auto trim) [DX3011]
MC9S08LL64CLH@LQFP64 [DX3011]　　MC9S08LL64CLK@QFP80 [DX3017]
MC9S08LL64MLH@LQFP64 [DX3011]　　MC9S08LL64MLK@QFP80 [DX3017]
MC9S08LL64VLH@LQFP64 [DX3011]　　MC9S08LL64VLK@QFP80 [DX3017]
MC9S08LL8CGT@QFN48 [DX4021]
MC9S08LL8CGT@QFN48(auto trim) [DX4021]
MC9S08LL8CLF@LQFP48 [DX3007]
MC9S08LL8CLF@LQFP48(auto trim) [DX3007]
MC9S08LL8CLH@LQFP64 [DX3011]
MC9S08LL8CLH@LQFP64(auto trim) [DX3011]
MC9S08LL8MGT@QFN48 [DX4021]
MC9S08LL8MGT@QFN48(auto trim) [DX4021]
MC9S08LL8MLF@LQFP48 [DX3007]
MC9S08LL8MLF@LQFP48(auto trim) [DX3007]
MC9S08LL8MLH@LQFP64 [DX3011]
MC9S08LL8MLH@LQFP64(auto trim) [DX3011]
MC9S08LL8VGT@QFN48 [DX4021]
MC9S08LL8VGT@QFN48(auto trim) [DX4021]
MC9S08LL8VLF@LQFP48 [DX3007]
MC9S08LL8VLF@LQFP48(auto trim) [DX3007]
MC9S08LL8VLH@LQFP64 [DX3011]
MC9S08LL8VLH@LQFP64(auto trim) [DX3011]
MC9S08MP12CLC@QFP32 [DX3001]　　MC9S08MP12CLF@QFP48 [DX3007]
MC9S08MP12CWL@SOIC28 [DX1033]　　MC9S08MP12MLC@QFP32 [DX3001]
MC9S08MP12MLF@QFP48 [DX3007]　　MC9S08MP12MWL@SOIC28 [DX1033]
MC9S08MP12VLC@QFP32 [DX3001]　　MC9S08MP12VLF@QFP48 [DX3007]
MC9S08MP12VWL@SOIC28 [DX1033]　　MC9S08MP16CLC@QFP32 [DX3001]
MC9S08MP16CLF@QFP48 [DX3007]　　MC9S08MP16CWL@SOIC28 [DX1033]
MC9S08MP16MLC@QFP32 [DX3001]　　MC9S08MP16MLF@QFP48 [DX3007]
MC9S08MP16MWL@SOIC28 [DX1033]　　MC9S08MP16VLC@QFP32 [DX3001]
MC9S08MP16VLF@QFP48 [DX3007]　　MC9S08MP16VWL@SOIC28 [DX1033]
MC9S08PA16CLC [DX3001]　　MC9S08PA16CLD [DX3005]
MC9S08PA16CTG [DX1000]　　MC9S08PA16CTJ [DX1000]
MC9S08PA16CWJ [DX1033]　　MC9S08PA16VLC [DX3001]

MC9S08PA16VLD [DX3005]
MC9S08PA16VTG [DX1000]
MC9S08PA16VTJ [DX1000]
MC9S08PA16VWJ [DX1033]
MC9S08PA32CLC [DX3001]
MC9S08PA32CLD [DX3005]
MC9S08PA32CLF [DX3007]
MC9S08PA32CLH [DX3011]
MC9S08PA32CQH [DX3014]
MC9S08PA32VLC [DX3001]
MC9S08PA32VLD [DX3005]
MC9S08PA32VLF [DX3007]
MC9S08PA32VLH [DX3011]
MC9S08PA32VQH [DX3014]
MC9S08PA60CLC [DX3001]
MC9S08PA60CLD [DX3005]
MC9S08PA60CLF [DX3007]
MC9S08PA60CLH [DX3011]
MC9S08PA60CQH [DX3014]
MC9S08PA60VLC [DX3001]
MC9S08PA60VLD [DX3005]
MC9S08PA60VLF [DX3007]
MC9S08PA60VLH [DX3011]
MC9S08PA60VQH [DX3014]
MC9S08PA8CLC [DX3001]
MC9S08PA8CLD [DX3005]
MC9S08PA8CTG [DX1000]
MC9S08PA8CTJ [DX1000]
MC9S08PA8CWJ [DX1033]
MC9S08PA8VLC [DX3001]
MC9S08PA8VLD [DX3005]
MC9S08PA8VTG [DX1000]
MC9S08PA8VTJ [DX1000]
MC9S08PA8VWJ [DX1033]
MC9S08PT16CLC [DX3001]
MC9S08PT16CLD [DX3005]
MC9S08PT16CTG [DX1000]
MC9S08PT16CTJ [DX1000]
MC9S08PT16CWJ [DX1033]
MC9S08PT16VLC [DX3001]
MC9S08PT16VLD [DX3005]
MC9S08PT16VTG [DX1000]
MC9S08PT16VTJ [DX1000]
MC9S08PT16VWJ [DX1033]
MC9S08PT32CLC [DX3001]
MC9S08PT32CLD [DX3005]
MC9S08PT32CLF [DX3007]
MC9S08PT32CLH [DX3011]
MC9S08PT32CQH [DX3014]
MC9S08PT32VLC [DX3001]
MC9S08PT32VLD [DX3005]
MC9S08PT32VLF [DX3007]
MC9S08PT32VLH [DX3011]
MC9S08PT32VQH [DX3014]
MC9S08PT60CLC [DX3001]
MC9S08PT60CLD [DX3005]
MC9S08PT60CLF [DX3007]
MC9S08PT60CLH [DX3011]
MC9S08PT60CQH [DX3014]
MC9S08PT60VLC [DX3001]
MC9S08PT60VLD [DX3005]
MC9S08PT60VLF [DX3007]
MC9S08PT60VLH [DX3011]
MC9S08PT60VQH [DX3014]
MC9S08PT8CLC [DX3001]
MC9S08PT8CLD [DX3005]
MC9S08PT8CTG [DX1000]
MC9S08PT8CTJ [DX1000]
MC9S08PT8CWJ [DX1033]
MC9S08PT8VLC [DX3001]
MC9S08PT8VLD [DX3005]
MC9S08PT8VTG [DX1000]
MC9S08PT8VTJ [DX1000]
MC9S08PT8VWJ [DX1033]
MC9S08QA2CDN@SOIC8 [DX1030]
MC9S08QA2CDNE@SOIC8 [DX1030]
MC9S08QA2CFQ@DFN8 [DX4004]
MC9S08QA2CFQE@DFN8 [DX4004]
MC9S08QA2CPA
MC9S08QA2CPAE
MC9S08QA2MDN@SOIC8 [DX1030]
MC9S08QA2MDNE@SOIC8 [DX1030]
MC9S08QA2MFQ@DFN8 [DX4004]
MC9S08QA2MFQE@DFN8 [DX4004]
MC9S08QA2MPA
MC9S08QA2MPAE
MC9S08QA2VDN@SOIC8 [DX1030]
MC9S08QA2VDNE@SOIC8 [DX1030]
MC9S08QA2VFQ@DFN8 [DX4004]
MC9S08QA2VFQE@DFN8 [DX4004]
MC9S08QA2VPA
MC9S08QA2VPAE
MC9S08QA4CDN@SOIC8 [DX1030]
MC9S08QA4CDNE@SOIC8 [DX1030]
MC9S08QA4CFQ@DFN8 [DX4004]
MC9S08QA4CFQE@DFN8 [DX4004]

MC9S08QA4CPA
MC9S08QA4CPAE
MC9S08QA4MDN@SOIC8 [DX1030]
MC9S08QA4MDNE@SOIC8 [DX1030]
MC9S08QA4MFQ@DFN8 [DX4004]
MC9S08QA4MFQE@DFN8 [DX4004]
MC9S08QA4MPA
MC9S08QA4MPAE
MC9S08QA4VDN@SOIC8 [DX1030]
MC9S08QA4VDNE@SOIC8 [DX1030]
MC9S08QA4VFQ@DFN8 [DX4004]
MC9S08QA4VFQE@DFN8 [DX4004]
MC9S08QA4VPA
MC9S08QA4VPAE
MC9S08QB4CGK@QFN24 [DX4034]
MC9S08QB4CTG@TSSOP16 [DX1001]
MC9S08QB4CWL@SOIC28 [DX1033]
MC9S08QB4MGK@QFN24 [DX4034]
MC9S08QB4MTG@TSSOP16 [DX1001]
MC9S08QB4MWL@SOIC28 [DX1033]
MC9S08QB4VGK@QFN24 [DX4034]
MC9S08QB4VTG@TSSOP16 [DX1001]
MC9S08QB4VWL@SOIC28 [DX1033]
MC9S08QB8CGK@QFN24 [DX4034]
MC9S08QB8CTG@TSSOP16 [DX1001]
MC9S08QB8CWL@SOIC28 [DX1033]
MC9S08QB8MGK@QFN24 [DX4034]
MC9S08QB8MTG@TSSOP16 [DX1001]
MC9S08QB8MWL@SOIC28 [DX1033]
MC9S08QB8VGK@QFN24 [DX4034]
MC9S08QB8VTG@TSSOP16 [DX1001]
MC9S08QB8VWL@SOIC28 [DX1033]
MC9S08QD2CPC
MC9S08QD2CPC(auto trim)
MC9S08QD2CPCE
MC9S08QD2CPCE(auto trim)
MC9S08QD2CSC@SOIC8 [DX1016]
MC9S08QD2CSC@SOIC8(auto trim) [DX1016]
MC9S08QD2CSCE@SOIC8 [DX1016]
MC9S08QD2CSCE@SOIC8(auto trim) [DX1016]
MC9S08QD2MPC
MC9S08QD2MPC(auto trim)
MC9S08QD2MPCE
MC9S08QD2MPCE(auto trim)
MC9S08QD2MSC@SOIC8 [DX1016]
MC9S08QD2MSC@SOIC8(auto trim) [DX1016]
MC9S08QD2MSCE@SOIC8 [DX1016]
MC9S08QD2MSCE@SOIC8(auto trim) [DX1016]
MC9S08QD2VPC
MC9S08QD2VPC(auto trim)
MC9S08QD2VPCE
MC9S08QD2VPCE(auto trim)
MC9S08QD2VSC@SOIC8 [DX1016]
MC9S08QD2VSC@SOIC8(auto trim) [DX1016]
MC9S08QD2VSCE@SOIC8 [DX1016]
MC9S08QD2VSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4CPC
MC9S08QD4CPC(auto trim)
MC9S08QD4CPCE
MC9S08QD4CPCE(auto trim)
MC9S08QD4CSC@SOIC8 [DX1016]
MC9S08QD4CSC@SOIC8(auto trim) [DX1016]
MC9S08QD4CSCE@SOIC8 [DX1016]
MC9S08QD4CSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4MPC
MC9S08QD4MPC(auto trim)
MC9S08QD4MPCE
MC9S08QD4MPCE(auto trim)
MC9S08QD4MSC@SOIC8 [DX1016]
MC9S08QD4MSC@SOIC8(auto trim) [DX1016]
MC9S08QD4MSCE@SOIC8 [DX1016]
MC9S08QD4MSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4VPC
MC9S08QD4VPC(auto trim)
MC9S08QD4VPCE
MC9S08QD4VPCE(auto trim)

MC9S08QD4VSC@SOIC8 [DX1016]
MC9S08QD4VSC@SOIC8(auto trim) [DX1016]
MC9S08QD4VSCE@SOIC8 [DX1016]
MC9S08QD4VSCE@SOIC8(auto trim) [DX1016]
MC9S08QE128CFT@QFN48 [DX4021]　　MC9S08QE128CFTE@QFN48 [DX4021]
MC9S08QE128CLC@QFP32 [DX3001]　　MC9S08QE128CLCE@QFP32 [DX3001]
MC9S08QE128CLD@QFP44 [DX3005]　　MC9S08QE128CLDE@QFP44 [DX3005]
MC9S08QE128CLH@QFP64 [DX3011]　　MC9S08QE128CLHE@QFP64 [DX3011]
MC9S08QE128CLK@QFP80 [DX3017]　　MC9S08QE128CLKE@QFP80 [DX3017]
MC9S08QE128MFT@QFN48 [DX4021]　　MC9S08QE128MFTE@QFN48 [DX4021]
MC9S08QE128MLC@QFP32 [DX3001]　　MC9S08QE128MLCE@QFP32 [DX3001]
MC9S08QE128MLD@QFP44 [DX3005]　　MC9S08QE128MLDE@QFP44 [DX3005]
MC9S08QE128MLH@QFP64 [DX3011]　　MC9S08QE128MLHE@QFP64 [DX3011]
MC9S08QE128MLK@QFP80 [DX3017]　　MC9S08QE128MLKE@QFP80 [DX3017]
MC9S08QE128VFT@QFN48 [DX4021]　　MC9S08QE128VFTE@QFN48 [DX4021]
MC9S08QE128VLC@QFP32 [DX3001]　　MC9S08QE128VLCE@QFP32 [DX3001]
MC9S08QE128VLD@QFP44 [DX3005]　　MC9S08QE128VLDE@QFP44 [DX3005]
MC9S08QE128VLH@QFP64 [DX3011]　　MC9S08QE128VLHE@QFP64 [DX3011]
MC9S08QE128VLK@QFP80 [DX3017]　　MC9S08QE128VLKE@QFP80 [DX3017]
MC9S08QE16CFT@QFN48 [DX4021]
MC9S08QE16CFT@QFN48(auto trim) [DX4021]
MC9S08QE16CFTE@QFN48 [DX4021]
MC9S08QE16CFTE@QFN48(auto trim) [DX4021]
MC9S08QE16CLC@QFP32 [DX3001]
MC9S08QE16CLC@QFP32(auto trim) [DX3001]
MC9S08QE16CLCE@QFP32 [DX3001]
MC9S08QE16CLCE@QFP32(auto trim) [DX3001]
MC9S08QE16CLD@QFP44 [DX3005]
MC9S08QE16CLD@QFP44(auto trim) [DX3005]
MC9S08QE16CLDE@QFP44 [DX3005]
MC9S08QE16CLDE@QFP44(auto trim) [DX3005]
MC9S08QE16CWL@SOIC28 [DX1033]
MC9S08QE16CWL@SOIC28(auto trim) [DX1033]
MC9S08QE16CWLE@SOIC28 [DX1033]
MC9S08QE16CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE16MFT@QFN48 [DX4021]
MC9S08QE16MFT@QFN48(auto trim) [DX4021]
MC9S08QE16MFTE@QFN48 [DX4021]
MC9S08QE16MFTE@QFN48(auto trim) [DX4021]
MC9S08QE16MLC@QFP32 [DX3001]
MC9S08QE16MLC@QFP32(auto trim) [DX3001]
MC9S08QE16MLCE@QFP32 [DX3001]
MC9S08QE16MLCE@QFP32(auto trim) [DX3001]
MC9S08QE16MLD@QFP44 [DX3005]
MC9S08QE16MLD@QFP44(auto trim) [DX3005]
MC9S08QE16MLDE@QFP44 [DX3005]
MC9S08QE16MLDE@QFP44(auto trim) [DX3005]
MC9S08QE16MWL@SOIC28 [DX1033]

MC9S08QE16MWL@SOIC28(auto trim) [DX1033]
MC9S08QE16MWLE@SOIC28 [DX1033]
MC9S08QE16MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE16VFT@QFN48 [DX4021]
MC9S08QE16VFT@QFN48(auto trim) [DX4021]
MC9S08QE16VFTE@QFN48 [DX4021]
MC9S08QE16VFTE@QFN48(auto trim) [DX4021]
MC9S08QE16VLC@QFP32 [DX3001]
MC9S08QE16VLC@QFP32(auto trim) [DX3001]
MC9S08QE16VLCE@QFP32 [DX3001]
MC9S08QE16VLCE@QFP32(auto trim) [DX3001]
MC9S08QE16VLD@QFP44 [DX3005]
MC9S08QE16VLD@QFP44(auto trim) [DX3005]
MC9S08QE16VLDE@QFP44 [DX3005]
MC9S08QE16VLDE@QFP44(auto trim) [DX3005]
MC9S08QE16VWL@SOIC28 [DX1033]
MC9S08QE16VWL@SOIC28(auto trim) [DX1033]
MC9S08QE16VWLE@SOIC28 [DX1033]
MC9S08QE16VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32CFT@QFN48 [DX4021]
MC9S08QE32CFT@QFN48(auto trim) [DX4021]
MC9S08QE32CFTE@QFN48 [DX4021]
MC9S08QE32CFTE@QFN48(auto trim) [DX4021]
MC9S08QE32CLC@QFP32 [DX3001]
MC9S08QE32CLC@QFP32(auto trim) [DX3001]
MC9S08QE32CLCE@QFP32 [DX3001]
MC9S08QE32CLCE@QFP32(auto trim) [DX3001]
MC9S08QE32CLD@QFP44 [DX3005]
MC9S08QE32CLD@QFP44(auto trim) [DX3005]
MC9S08QE32CLDE@QFP44 [DX3005]
MC9S08QE32CLDE@QFP44(auto trim) [DX3005]
MC9S08QE32CWL@SOIC28 [DX1033]
MC9S08QE32CWL@SOIC28(auto trim) [DX1033]
MC9S08QE32CWLE@SOIC28 [DX1033]
MC9S08QE32CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32MFT@QFN48 [DX4021]
MC9S08QE32MFT@QFN48(auto trim) [DX4021]
MC9S08QE32MFTE@QFN48 [DX4021]
MC9S08QE32MFTE@QFN48(auto trim) [DX4021]
MC9S08QE32MLC@QFP32 [DX3001]
MC9S08QE32MLC@QFP32(auto trim) [DX3001]
MC9S08QE32MLCE@QFP32 [DX3001]
MC9S08QE32MLCE@QFP32(auto trim) [DX3001]
MC9S08QE32MLD@QFP44 [DX3005]
MC9S08QE32MLD@QFP44(auto trim) [DX3005]
MC9S08QE32MLDE@QFP44 [DX3005]
MC9S08QE32MLDE@QFP44(auto trim) [DX3005]
MC9S08QE32MWL@SOIC28 [DX1033]

MC9S08QE32MWL@SOIC28(auto trim) [DX1033]
MC9S08QE32MWLE@SOIC28 [DX1033]
MC9S08QE32MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32VFT@QFN48 [DX4021]
MC9S08QE32VFT@QFN48(auto trim) [DX4021]
MC9S08QE32VFTE@QFN48 [DX4021]
MC9S08QE32VFTE@QFN48(auto trim) [DX4021]
MC9S08QE32VLC@QFP32 [DX3001]
MC9S08QE32VLC@QFP32(auto trim) [DX3001]
MC9S08QE32VLCE@QFP32 [DX3001]
MC9S08QE32VLCE@QFP32(auto trim) [DX3001]
MC9S08QE32VLD@QFP44 [DX3005]
MC9S08QE32VLD@QFP44(auto trim) [DX3005]
MC9S08QE32VLDE@QFP44 [DX3005]
MC9S08QE32VLDE@QFP44(auto trim) [DX3005]
MC9S08QE32VWL@SOIC28 [DX1033]
MC9S08QE32VWL@SOIC28(auto trim) [DX1033]
MC9S08QE32VWLE@SOIC28 [DX1033]
MC9S08QE32VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4CLC@QFP32 [DX3001]
MC9S08QE4CLC@QFP32(auto trim) [DX3001]
MC9S08QE4CLCE@QFP32 [DX3001]
MC9S08QE4CLCE@QFP32(auto trim) [DX3001]
MC9S08QE4CPG MC9S08QE4CPG(auto trim)
MC9S08QE4CPGE MC9S08QE4CPGE(auto trim)
MC9S08QE4CTG@TSSOP16 [DX1000]
MC9S08QE4CTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4CTGE@TSSOP16 [DX1000]
MC9S08QE4CTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4CWJ@SOIC20 [DX1033]
MC9S08QE4CWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4CWJE@SOIC20 [DX1033]
MC9S08QE4CWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4CWL@SOIC28 [DX1033]
MC9S08QE4CWL@SOIC28(auto trim) [DX1033]
MC9S08QE4CWLE@SOIC28 [DX1033]
MC9S08QE4CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4MLC@QFP32 [DX3001]
MC9S08QE4MLC@QFP32(auto trim) [DX3001]
MC9S08QE4MLCE@QFP32 [DX3001]
MC9S08QE4MLCE@QFP32(auto trim) [DX3001]
MC9S08QE4MPG MC9S08QE4MPG(auto trim)
MC9S08QE4MPGE MC9S08QE4MPGE(auto trim)
MC9S08QE4MTG@TSSOP16 [DX1000]
MC9S08QE4MTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4MTGE@TSSOP16 [DX1000]
MC9S08QE4MTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4MWJ@SOIC20 [DX1033]

MC9S08QE4MWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4MWJE@SOIC20 [DX1033]
MC9S08QE4MWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4MWL@SOIC28 [DX1033]
MC9S08QE4MWL@SOIC28(auto trim) [DX1033]
MC9S08QE4MWLE@SOIC28 [DX1033]
MC9S08QE4MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4VLC@QFP32 [DX3001]
MC9S08QE4VLC@QFP32(auto trim) [DX3001]
MC9S08QE4VLCE@QFP32 [DX3001]
MC9S08QE4VLCE@QFP32(auto trim) [DX3001]
MC9S08QE4VPG MC9S08QE4VPG(auto trim)
MC9S08QE4VPGE MC9S08QE4VPGE(auto trim)
MC9S08QE4VTG@TSSOP16 [DX1000]
MC9S08QE4VTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4VTGE@TSSOP16 [DX1000]
MC9S08QE4VTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4VWJ@SOIC20 [DX1033]
MC9S08QE4VWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4VWJE@SOIC20 [DX1033]
MC9S08QE4VWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4VWL@SOIC28 [DX1033]
MC9S08QE4VWL@SOIC28(auto trim) [DX1033]
MC9S08QE4VWLE@SOIC28 [DX1033]
MC9S08QE4VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE64CFT@QFN48 [DX4021] MC9S08QE64CFTE@QFN48 [DX4021]
MC9S08QE64CLC@QFP32 [DX3001] MC9S08QE64CLCE@QFP32 [DX3001]
MC9S08QE64CLD@QFP44 [DX3005] MC9S08QE64CLDE@QFP44 [DX3005]
MC9S08QE64CLH@QFP64 [DX3011] MC9S08QE64CLHE@QFP64 [DX3011]
MC9S08QE64CLK@QFP80 [DX3017] MC9S08QE64CLKE@QFP80 [DX3017]
MC9S08QE64MFT@QFN48 [DX4021] MC9S08QE64MFTE@QFN48 [DX4021]
MC9S08QE64MLC@QFP32 [DX3001] MC9S08QE64MLCE@QFP32 [DX3001]
MC9S08QE64MLD@QFP44 [DX3005] MC9S08QE64MLDE@QFP44 [DX3005]
MC9S08QE64MLH@QFP64 [DX3011] MC9S08QE64MLHE@QFP64 [DX3011]
MC9S08QE64MLK@QFP80 [DX3017] MC9S08QE64MLKE@QFP80 [DX3017]
MC9S08QE64VFT@QFN48 [DX4021] MC9S08QE64VFTE@QFN48 [DX4021]
MC9S08QE64VLC@QFP32 [DX3001] MC9S08QE64VLCE@QFP32 [DX3001]
MC9S08QE64VLD@QFP44 [DX3005] MC9S08QE64VLDE@QFP44 [DX3005]
MC9S08QE64VLH@QFP64 [DX3011] MC9S08QE64VLHE@QFP64 [DX3011]
MC9S08QE64VLK@QFP80 [DX3017] MC9S08QE64VLKE@QFP80 [DX3017]
MC9S08QE8CLC@QFP32 [DX3001]
MC9S08QE8CLC@QFP32(auto trim) [DX3001]
MC9S08QE8CLCE@QFP32 [DX3001]
MC9S08QE8CLCE@QFP32(auto trim) [DX3001]
MC9S08QE8CPG MC9S08QE8CPG(auto trim)
MC9S08QE8CPGE MC9S08QE8CPGE(auto trim)
MC9S08QE8CTG@TSSOP16 [DX1000]
MC9S08QE8CTG@TSSOP16(auto trim) [DX1000]

MC9S08QE8CTGE@TSSOP16 [DX1000]
MC9S08QE8CTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE8CWJ@SOIC20 [DX1033]
MC9S08QE8CWJ@SOIC20(auto trim) [DX1033]
MC9S08QE8CWJE@SOIC20 [DX1033]
MC9S08QE8CWJE@SOIC20(auto trim) [DX1033]
MC9S08QE8CWL@SOIC28 [DX1033]
MC9S08QE8CWL@SOIC28(auto trim) [DX1033]
MC9S08QE8CWLE@SOIC28 [DX1033]
MC9S08QE8CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE8MLC@QFP32 [DX3001]
MC9S08QE8MLC@QFP32(auto trim) [DX3001]
MC9S08QE8MLCE@QFP32 [DX3001]
MC9S08QE8MLCE@QFP32(auto trim) [DX3001]
MC9S08QE8MPG MC9S08QE8MPG(auto trim)
MC9S08QE8MPGE MC9S08QE8MPGE(auto trim)
MC9S08QE8MTG@TSSOP16 [DX1000]
MC9S08QE8MTG@TSSOP16(auto trim) [DX1000]
MC9S08QE8MTGE@TSSOP16 [DX1000]
MC9S08QE8MTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE8MWJ@SOIC20 [DX1033]
MC9S08QE8MWJ@SOIC20(auto trim) [DX1033]
MC9S08QE8MWJE@SOIC20 [DX1033]
MC9S08QE8MWJE@SOIC20(auto trim) [DX1033]
MC9S08QE8MWL@SOIC28 [DX1033]
MC9S08QE8MWL@SOIC28(auto trim) [DX1033]
MC9S08QE8MWLE@SOIC28 [DX1033]
MC9S08QE8MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE8VLC@QFP32 [DX3001]
MC9S08QE8VLC@QFP32(auto trim) [DX3001]
MC9S08QE8VLCE@QFP32 [DX3001]
MC9S08QE8VLCE@QFP32(auto trim) [DX3001]
MC9S08QE8VPG MC9S08QE8VPG(auto trim)
MC9S08QE8VPGE MC9S08QE8VPGE(auto trim)
MC9S08QE8VTG@TSSOP16 [DX1000]
MC9S08QE8VTG@TSSOP16(auto trim) [DX1000]
MC9S08QE8VTGE@TSSOP16 [DX1000]
MC9S08QE8VTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE8VWJ@SOIC20 [DX1033]
MC9S08QE8VWJ@SOIC20(auto trim) [DX1033]
MC9S08QE8VWJE@SOIC20 [DX1033]
MC9S08QE8VWJE@SOIC20(auto trim) [DX1033]
MC9S08QE8VWL@SOIC28 [DX1033]
MC9S08QE8VWL@SOIC28(auto trim) [DX1033]
MC9S08QE8VWLE@SOIC28 [DX1033]
MC9S08QE8VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE96CFT@QFN48 [DX4021] MC9S08QE96CFTE@QFN48 [DX4021]
MC9S08QE96CLC@QFP32 [DX3001] MC9S08QE96CLCE@QFP32 [DX3001]

MC9S08QE96CLD@QFP44 [DX3005]	MC9S08QE96CLDE@QFP44 [DX3005]
MC9S08QE96CLH@QFP64 [DX3011]	MC9S08QE96CLHE@QFP64 [DX3011]
MC9S08QE96CLK@QFP80 [DX3017]	MC9S08QE96CLKE@QFP80 [DX3017]
MC9S08QE96MFT@QFN48 [DX4021]	MC9S08QE96MFTE@QFN48 [DX4021]
MC9S08QE96MLC@QFP32 [DX3001]	MC9S08QE96MLCE@QFP32 [DX3001]
MC9S08QE96MLD@QFP44 [DX3005]	MC9S08QE96MLDE@QFP44 [DX3005]
MC9S08QE96MLH@QFP64 [DX3011]	MC9S08QE96MLHE@QFP64 [DX3011]
MC9S08QE96MLK@QFP80 [DX3017]	MC9S08QE96MLKE@QFP80 [DX3017]
MC9S08QE96VFT@QFN48 [DX4021]	MC9S08QE96VFTE@QFN48 [DX4021]
MC9S08QE96VLC@QFP32 [DX3001]	MC9S08QE96VLCE@QFP32 [DX3001]
MC9S08QE96VLD@QFP44 [DX3005]	MC9S08QE96VLDE@QFP44 [DX3005]
MC9S08QE96VLH@QFP64 [DX3011]	MC9S08QE96VLHE@QFP64 [DX3011]
MC9S08QE96VLK@QFP80 [DX3017]	MC9S08QE96VLKE@QFP80 [DX3017]
MC9S08QG4CDN@SOIC8 [DX1030]	MC9S08QG4CDNE@SOIC8 [DX1030]
MC9S08QG4CDT@TSSOP16 [DX1000]	MC9S08QG4CDTE@TSSOP16 [DX1000]
MC9S08QG4CFF@QFN16 [DX4009]	MC9S08QG4CFFE@QFN16 [DX4009]
MC9S08QG4CFQ@DFN8 [DX4004]	MC9S08QG4CFQE@DFN8 [DX4004]
MC9S08QG4CPA	MC9S08QG4CPAE
MC9S08QG4MDN@SOIC8 [DX1030]	MC9S08QG4MDNE@SOIC8 [DX1030]
MC9S08QG4MDT@TSSOP16 [DX1000]	MC9S08QG4MDTE@TSSOP16 [DX1000]
MC9S08QG4MFF@QFN16 [DX4009]	MC9S08QG4MFFE@QFN16 [DX4009]
MC9S08QG4MFQ@DFN8 [DX4004]	MC9S08QG4MFQE@DFN8 [DX4004]
MC9S08QG4MPA	MC9S08QG4MPAE
MC9S08QG4VDN@SOIC8 [DX1030]	MC9S08QG4VDNE@SOIC8 [DX1030]
MC9S08QG4VDT@TSSOP16 [DX1000]	MC9S08QG4VDTE@TSSOP16 [DX1000]
MC9S08QG4VFF@QFN16 [DX4009]	MC9S08QG4VFFE@QFN16 [DX4009]
MC9S08QG4VFQ@DFN8 [DX4004]	MC9S08QG4VFQE@DFN8 [DX4004]
MC9S08QG4VPA	MC9S08QG4VPAE
MC9S08QG8CDN@SOIC8 [DX1030]	MC9S08QG8CDNE@SOIC8 [DX1030]
MC9S08QG8CDT@TSSOP16 [DX1000]	MC9S08QG8CDTE@TSSOP16 [DX1000]
MC9S08QG8CFF@QFN16 [DX4009]	MC9S08QG8CFFE@QFN16 [DX4009]
MC9S08QG8CFQ@DFN8 [DX4004]	MC9S08QG8CFQE@DFN8 [DX4004]
MC9S08QG8CPB	MC9S08QG8CPBE
MC9S08QG8MDN@SOIC8 [DX1030]	MC9S08QG8MDNE@SOIC8 [DX1030]
MC9S08QG8MDT@TSSOP16 [DX1000]	MC9S08QG8MDTE@TSSOP16 [DX1000]
MC9S08QG8MFF@QFN16 [DX4009]	MC9S08QG8MFFE@QFN16 [DX4009]
MC9S08QG8MFQ@DFN8 [DX4004]	MC9S08QG8MFQE@DFN8 [DX4004]
MC9S08QG8MPB	MC9S08QG8MPBE
MC9S08QG8VDN@SOIC8 [DX1030]	MC9S08QG8VDNE@SOIC8 [DX1030]
MC9S08QG8VDT@TSSOP16 [DX1000]	MC9S08QG8VDTE@TSSOP16 [DX1000]
MC9S08QG8VFF@QFN16 [DX4009]	MC9S08QG8VFFE@QFN16 [DX4009]
MC9S08QG8VFQ@DFN8 [DX4004]	MC9S08QG8VFQE@DFN8 [DX4004]
MC9S08QG8VPB	MC9S08QG8VPBE
MC9S08RC16CDW@SOIC28 [DX1033]	MC9S08RC16CDWE@SOIC28 [DX1033]
MC9S08RC16CFD@QFN48 [DX4021]	MC9S08RC16CFDE@QFN48 [DX4021]
MC9S08RC16CFG@LQFP44 [DX3003]	MC9S08RC16CFGE@LQFP44 [DX3003]
MC9S08RC16CFJ@LQFP32 [DX3001]	MC9S08RC16CFJE@LQFP32 [DX3001]
MC9S08RC16CP	MC9S08RC16CPE

MC9S08RC16MDW@SOIC28 [DX1033]	MC9S08RC16MDWE@SOIC28 [DX1033]
MC9S08RC16MFD@QFN48 [DX4021]	MC9S08RC16MFDE@QFN48 [DX4021]
MC9S08RC16MFG@LQFP44 [DX3003]	MC9S08RC16MFGE@LQFP44 [DX3003]
MC9S08RC16MFJ@LQFP32 [DX3001]	MC9S08RC16MFJE@LQFP32 [DX3001]
MC9S08RC16MP	MC9S08RC16MPE
MC9S08RC16VDW@SOIC28 [DX1033]	MC9S08RC16VDWE@SOIC28 [DX1033]
MC9S08RC16VFD@QFN48 [DX4021]	MC9S08RC16VFDE@QFN48 [DX4021]
MC9S08RC16VFG@LQFP44 [DX3003]	MC9S08RC16VFGE@LQFP44 [DX3003]
MC9S08RC16VFJ@LQFP32 [DX3001]	MC9S08RC16VFJE@LQFP32 [DX3001]
MC9S08RC16VP	MC9S08RC16VPE
MC9S08RC32CDW@SOIC28 [DX1033]	MC9S08RC32CDWE@SOIC28 [DX1033]
MC9S08RC32CFD@QFN48 [DX4021]	MC9S08RC32CFDE@QFN48 [DX4021]
MC9S08RC32CFG@LQFP44 [DX3003]	MC9S08RC32CFGE@LQFP44 [DX3003]
MC9S08RC32CFJ@LQFP32 [DX3001]	MC9S08RC32CFJE@LQFP32 [DX3001]
MC9S08RC32CP	MC9S08RC32CPE
MC9S08RC32MDW@SOIC28 [DX1033]	MC9S08RC32MDWE@SOIC28 [DX1033]
MC9S08RC32MFD@QFN48 [DX4021]	MC9S08RC32MFDE@QFN48 [DX4021]
MC9S08RC32MFG@LQFP44 [DX3003]	MC9S08RC32MFGE@LQFP44 [DX3003]
MC9S08RC32MFJ@LQFP32 [DX3001]	MC9S08RC32MFJE@LQFP32 [DX3001]
MC9S08RC32MP	MC9S08RC32MPE
MC9S08RC32VDW@SOIC28 [DX1033]	MC9S08RC32VDWE@SOIC28 [DX1033]
MC9S08RC32VFD@QFN48 [DX4021]	MC9S08RC32VFDE@QFN48 [DX4021]
MC9S08RC32VFG@LQFP44 [DX3003]	MC9S08RC32VFGE@LQFP44 [DX3003]
MC9S08RC32VFJ@LQFP32 [DX3001]	MC9S08RC32VFJE@LQFP32 [DX3001]
MC9S08RC32VP	MC9S08RC32VPE
MC9S08RC60CDW@SOIC28 [DX1033]	MC9S08RC60CDWE@SOIC28 [DX1033]
MC9S08RC60CFD@QFN48 [DX4021]	MC9S08RC60CFDE@QFN48 [DX4021]
MC9S08RC60CFG@LQFP44 [DX3003]	MC9S08RC60CFGE@LQFP44 [DX3003]
MC9S08RC60CFJ@LQFP32 [DX3001]	MC9S08RC60CFJE@LQFP32 [DX3001]
MC9S08RC60CP	MC9S08RC60CPE
MC9S08RC60MDW@SOIC28 [DX1033]	MC9S08RC60MDWE@SOIC28 [DX1033]
MC9S08RC60MFD@QFN48 [DX4021]	MC9S08RC60MFDE@QFN48 [DX4021]
MC9S08RC60MFG@LQFP44 [DX3003]	MC9S08RC60MFGE@LQFP44 [DX3003]
MC9S08RC60MFJ@LQFP32 [DX3001]	MC9S08RC60MFJE@LQFP32 [DX3001]
MC9S08RC60MP	MC9S08RC60MPE
MC9S08RC60VDW@SOIC28 [DX1033]	MC9S08RC60VDWE@SOIC28 [DX1033]
MC9S08RC60VFD@QFN48 [DX4021]	MC9S08RC60VFDE@QFN48 [DX4021]
MC9S08RC60VFG@LQFP44 [DX3003]	MC9S08RC60VFGE@LQFP44 [DX3003]
MC9S08RC60VFJ@LQFP32 [DX3001]	MC9S08RC60VFJE@LQFP32 [DX3001]
MC9S08RC60VP	MC9S08RC60VPE
MC9S08RC8CDW@SOIC28 [DX1033]	MC9S08RC8CDWE@SOIC28 [DX1033]
MC9S08RC8CFD@QFN48 [DX4021]	MC9S08RC8CFDE@QFN48 [DX4021]
MC9S08RC8CFG@LQFP44 [DX3003]	MC9S08RC8CFGE@LQFP44 [DX3003]
MC9S08RC8CFJ@LQFP32 [DX3001]	MC9S08RC8CFJE@LQFP32 [DX3001]
MC9S08RC8CP	MC9S08RC8CPE
MC9S08RC8MDW@SOIC28 [DX1033]	MC9S08RC8MDWE@SOIC28 [DX1033]
MC9S08RC8MFD@QFN48 [DX4021]	MC9S08RC8MFDE@QFN48 [DX4021]
MC9S08RC8MFG@LQFP44 [DX3003]	MC9S08RC8MFGE@LQFP44 [DX3003]

MC9S08RC8MFJ@LQFP32 [DX3001]	MC9S08RC8MFJE@LQFP32 [DX3001]
MC9S08RC8MP	MC9S08RC8MPE
MC9S08RC8VDW@SOIC28 [DX1033]	MC9S08RC8VDWE@SOIC28 [DX1033]
MC9S08RC8VFD@QFN48 [DX4021]	MC9S08RC8VFDE@QFN48 [DX4021]
MC9S08RC8VFG@LQFP44 [DX3003]	MC9S08RC8VFGE@LQFP44 [DX3003]
MC9S08RC8VFJ@LQFP32 [DX3001]	MC9S08RC8VFJE@LQFP32 [DX3001]
MC9S08RC8VP	MC9S08RC8VPE
MC9S08RD16CDW@SOIC28 [DX1033]	MC9S08RD16CDWE@SOIC28 [DX1033]
MC9S08RD16CFD@QFN48 [DX4021]	MC9S08RD16CFDE@QFN48 [DX4021]
MC9S08RD16CFG@LQFP44 [DX3003]	MC9S08RD16CFGE@LQFP44 [DX3003]
MC9S08RD16CFJ@LQFP32 [DX3001]	MC9S08RD16CFJE@LQFP32 [DX3001]
MC9S08RD16CP	MC9S08RD16CPE
MC9S08RD16MDW@SOIC28 [DX1033]	MC9S08RD16MDWE@SOIC28 [DX1033]
MC9S08RD16MFD@QFN48 [DX4021]	MC9S08RD16MFDE@QFN48 [DX4021]
MC9S08RD16MFG@LQFP44 [DX3003]	MC9S08RD16MFGE@LQFP44 [DX3003]
MC9S08RD16MFJ@LQFP32 [DX3001]	MC9S08RD16MFJE@LQFP32 [DX3001]
MC9S08RD16MP	MC9S08RD16MPE
MC9S08RD16VDW@SOIC28 [DX1033]	MC9S08RD16VDWE@SOIC28 [DX1033]
MC9S08RD16VFD@QFN48 [DX4021]	MC9S08RD16VFDE@QFN48 [DX4021]
MC9S08RD16VFG@LQFP44 [DX3003]	MC9S08RD16VFGE@LQFP44 [DX3003]
MC9S08RD16VFJ@LQFP32 [DX3001]	MC9S08RD16VFJE@LQFP32 [DX3001]
MC9S08RD16VP	MC9S08RD16VPE
MC9S08RD32CDW@SOIC28 [DX1033]	MC9S08RD32CDWE@SOIC28 [DX1033]
MC9S08RD32CFD@QFN48 [DX4021]	MC9S08RD32CFDE@QFN48 [DX4021]
MC9S08RD32CFG@LQFP44 [DX3003]	MC9S08RD32CFGE@LQFP44 [DX3003]
MC9S08RD32CFJ@LQFP32 [DX3001]	MC9S08RD32CFJE@LQFP32 [DX3001]
MC9S08RD32CP	MC9S08RD32CPE
MC9S08RD32MDW@SOIC28 [DX1033]	MC9S08RD32MDWE@SOIC28 [DX1033]
MC9S08RD32MFD@QFN48 [DX4021]	MC9S08RD32MFDE@QFN48 [DX4021]
MC9S08RD32MFG@LQFP44 [DX3003]	MC9S08RD32MFGE@LQFP44 [DX3003]
MC9S08RD32MFJ@LQFP32 [DX3001]	MC9S08RD32MFJE@LQFP32 [DX3001]
MC9S08RD32MP	MC9S08RD32MPE
MC9S08RD32VDW@SOIC28 [DX1033]	MC9S08RD32VDWE@SOIC28 [DX1033]
MC9S08RD32VFD@QFN48 [DX4021]	MC9S08RD32VFDE@QFN48 [DX4021]
MC9S08RD32VFG@LQFP44 [DX3003]	MC9S08RD32VFGE@LQFP44 [DX3003]
MC9S08RD32VFJ@LQFP32 [DX3001]	MC9S08RD32VFJE@LQFP32 [DX3001]
MC9S08RD32VP	MC9S08RD32VPE
MC9S08RD60CDW@SOIC28 [DX1033]	MC9S08RD60CDWE@SOIC28 [DX1033]
MC9S08RD60CFD@QFN48 [DX4021]	MC9S08RD60CFDE@QFN48 [DX4021]
MC9S08RD60CFG@LQFP44 [DX3003]	MC9S08RD60CFGE@LQFP44 [DX3003]
MC9S08RD60CFJ@LQFP32 [DX3001]	MC9S08RD60CFJE@LQFP32 [DX3001]
MC9S08RD60CP	MC9S08RD60CPE
MC9S08RD60MDW@SOIC28 [DX1033]	MC9S08RD60MDWE@SOIC28 [DX1033]
MC9S08RD60MFD@QFN48 [DX4021]	MC9S08RD60MFDE@QFN48 [DX4021]
MC9S08RD60MFG@LQFP44 [DX3003]	MC9S08RD60MFGE@LQFP44 [DX3003]
MC9S08RD60MFJ@LQFP32 [DX3001]	MC9S08RD60MFJE@LQFP32 [DX3001]
MC9S08RD60MP	MC9S08RD60MPE
MC9S08RD60VDW@SOIC28 [DX1033]	MC9S08RD60VDWE@SOIC28 [DX1033]

MC9S08RD60VFD@QFN48 [DX4021]	MC9S08RD60VFDE@QFN48 [DX4021]
MC9S08RD60VFG@LQFP44 [DX3003]	MC9S08RD60VFGE@LQFP44 [DX3003]
MC9S08RD60VFJ@LQFP32 [DX3001]	MC9S08RD60VFJE@LQFP32 [DX3001]
MC9S08RD60VP	MC9S08RD60VPE
MC9S08RD8CDW@SOIC28 [DX1033]	MC9S08RD8CDWE@SOIC28 [DX1033]
MC9S08RD8CFD@QFN48 [DX4021]	MC9S08RD8CFDE@QFN48 [DX4021]
MC9S08RD8CFG@LQFP44 [DX3003]	MC9S08RD8CFGE@LQFP44 [DX3003]
MC9S08RD8CFJ@LQFP32 [DX3001]	MC9S08RD8CFJE@LQFP32 [DX3001]
MC9S08RD8CP	MC9S08RD8CPE
MC9S08RD8MDW@SOIC28 [DX1033]	MC9S08RD8MDWE@SOIC28 [DX1033]
MC9S08RD8MFD@QFN48 [DX4021]	MC9S08RD8MFDE@QFN48 [DX4021]
MC9S08RD8MFG@LQFP44 [DX3003]	MC9S08RD8MFGE@LQFP44 [DX3003]
MC9S08RD8MFJ@LQFP32 [DX3001]	MC9S08RD8MFJE@LQFP32 [DX3001]
MC9S08RD8MP	MC9S08RD8MPE
MC9S08RD8VDW@SOIC28 [DX1033]	MC9S08RD8VDWE@SOIC28 [DX1033]
MC9S08RD8VFD@QFN48 [DX4021]	MC9S08RD8VFDE@QFN48 [DX4021]
MC9S08RD8VFG@LQFP44 [DX3003]	MC9S08RD8VFGE@LQFP44 [DX3003]
MC9S08RD8VFJ@LQFP32 [DX3001]	MC9S08RD8VFJE@LQFP32 [DX3001]
MC9S08RD8VP	MC9S08RD8VPE
MC9S08RE16CDW@SOIC28 [DX1033]	MC9S08RE16CDWE@SOIC28 [DX1033]
MC9S08RE16CFD@QFN48 [DX4021]	MC9S08RE16CFDE@QFN48 [DX4021]
MC9S08RE16CFG@LQFP44 [DX3003]	MC9S08RE16CFGE@LQFP44 [DX3003]
MC9S08RE16CFJ@LQFP32 [DX3001]	MC9S08RE16CFJE@LQFP32 [DX3001]
MC9S08RE16CP	MC9S08RE16CPE
MC9S08RE16MDW@SOIC28 [DX1033]	MC9S08RE16MDWE@SOIC28 [DX1033]
MC9S08RE16MFD@QFN48 [DX4021]	MC9S08RE16MFDE@QFN48 [DX4021]
MC9S08RE16MFG@LQFP44 [DX3003]	MC9S08RE16MFGE@LQFP44 [DX3003]
MC9S08RE16MFJ@LQFP32 [DX3001]	MC9S08RE16MFJE@LQFP32 [DX3001]
MC9S08RE16MP	MC9S08RE16MPE
MC9S08RE16VDW@SOIC28 [DX1033]	MC9S08RE16VDWE@SOIC28 [DX1033]
MC9S08RE16VFD@QFN48 [DX4021]	MC9S08RE16VFDE@QFN48 [DX4021]
MC9S08RE16VFG@LQFP44 [DX3003]	MC9S08RE16VFGE@LQFP44 [DX3003]
MC9S08RE16VFJ@LQFP32 [DX3001]	MC9S08RE16VFJE@LQFP32 [DX3001]
MC9S08RE16VP	MC9S08RE16VPE
MC9S08RE32CDW@SOIC28 [DX1033]	MC9S08RE32CDWE@SOIC28 [DX1033]
MC9S08RE32CFD@QFN48 [DX4021]	MC9S08RE32CFDE@QFN48 [DX4021]
MC9S08RE32CFG@LQFP44 [DX3003]	MC9S08RE32CFGE@LQFP44 [DX3003]
MC9S08RE32CFJ@LQFP32 [DX3001]	MC9S08RE32CFJE@LQFP32 [DX3001]
MC9S08RE32CP	MC9S08RE32CPE
MC9S08RE32MDW@SOIC28 [DX1033]	MC9S08RE32MDWE@SOIC28 [DX1033]
MC9S08RE32MFD@QFN48 [DX4021]	MC9S08RE32MFDE@QFN48 [DX4021]
MC9S08RE32MFG@LQFP44 [DX3003]	MC9S08RE32MFGE@LQFP44 [DX3003]
MC9S08RE32MFJ@LQFP32 [DX3001]	MC9S08RE32MFJE@LQFP32 [DX3001]
MC9S08RE32MP	MC9S08RE32MPE
MC9S08RE32VDW@SOIC28 [DX1033]	MC9S08RE32VDWE@SOIC28 [DX1033]
MC9S08RE32VFD@QFN48 [DX4021]	MC9S08RE32VFDE@QFN48 [DX4021]
MC9S08RE32VFG@LQFP44 [DX3003]	MC9S08RE32VFGE@LQFP44 [DX3003]
MC9S08RE32VFJ@LQFP32 [DX3001]	MC9S08RE32VFJE@LQFP32 [DX3001]

MC9S08RE32VP	MC9S08RE32VPE
MC9S08RE60CDW@SOIC28 [DX1033]	MC9S08RE60CDWE@SOIC28 [DX1033]
MC9S08RE60CFD@QFN48 [DX4021]	MC9S08RE60CFDE@QFN48 [DX4021]
MC9S08RE60CFG@LQFP44 [DX3003]	MC9S08RE60CFGE@LQFP44 [DX3003]
MC9S08RE60CFJ@LQFP32 [DX3001]	MC9S08RE60CFJE@LQFP32 [DX3001]
MC9S08RE60CP	MC9S08RE60CPE
MC9S08RE60MDW@SOIC28 [DX1033]	MC9S08RE60MDWE@SOIC28 [DX1033]
MC9S08RE60MFD@QFN48 [DX4021]	MC9S08RE60MFDE@QFN48 [DX4021]
MC9S08RE60MFG@LQFP44 [DX3003]	MC9S08RE60MFGE@LQFP44 [DX3003]
MC9S08RE60MFJ@LQFP32 [DX3001]	MC9S08RE60MFJE@LQFP32 [DX3001]
MC9S08RE60MP	MC9S08RE60MPE
MC9S08RE60VDW@SOIC28 [DX1033]	MC9S08RE60VDWE@SOIC28 [DX1033]
MC9S08RE60VFD@QFN48 [DX4021]	MC9S08RE60VFDE@QFN48 [DX4021]
MC9S08RE60VFG@LQFP44 [DX3003]	MC9S08RE60VFGE@LQFP44 [DX3003]
MC9S08RE60VFJ@LQFP32 [DX3001]	MC9S08RE60VFJE@LQFP32 [DX3001]
MC9S08RE60VP	MC9S08RE60VPE
MC9S08RE8CDW@SOIC28 [DX1033]	MC9S08RE8CDWE@SOIC28 [DX1033]
MC9S08RE8CFD@QFN48 [DX4021]	MC9S08RE8CFDE@QFN48 [DX4021]
MC9S08RE8CFG@LQFP44 [DX3003]	MC9S08RE8CFGE@LQFP44 [DX3003]
MC9S08RE8CFJ@LQFP32 [DX3001]	MC9S08RE8CFJE@LQFP32 [DX3001]
MC9S08RE8CP	MC9S08RE8CPE
MC9S08RE8MDW@SOIC28 [DX1033]	MC9S08RE8MDWE@SOIC28 [DX1033]
MC9S08RE8MFD@QFN48 [DX4021]	MC9S08RE8MFDE@QFN48 [DX4021]
MC9S08RE8MFG@LQFP44 [DX3003]	MC9S08RE8MFGE@LQFP44 [DX3003]
MC9S08RE8MFJ@LQFP32 [DX3001]	MC9S08RE8MFJE@LQFP32 [DX3001]
MC9S08RE8MP	MC9S08RE8MPE
MC9S08RE8VDW@SOIC28 [DX1033]	MC9S08RE8VDWE@SOIC28 [DX1033]
MC9S08RE8VFD@QFN48 [DX4021]	MC9S08RE8VFDE@QFN48 [DX4021]
MC9S08RE8VFG@LQFP44 [DX3003]	MC9S08RE8VFGE@LQFP44 [DX3003]
MC9S08RE8VFJ@LQFP32 [DX3001]	MC9S08RE8VFJE@LQFP32 [DX3001]
MC9S08RE8VP	MC9S08RE8VPE
MC9S08RG16CDW@SOIC28 [DX1033]	MC9S08RG16CDWE@SOIC28 [DX1033]
MC9S08RG16CFD@QFN48 [DX4021]	MC9S08RG16CFDE@QFN48 [DX4021]
MC9S08RG16CFG@LQFP44 [DX3003]	MC9S08RG16CFGE@LQFP44 [DX3003]
MC9S08RG16CFJ@LQFP32 [DX3001]	MC9S08RG16CFJE@LQFP32 [DX3001]
MC9S08RG16CP	MC9S08RG16CPE
MC9S08RG16MDW@SOIC28 [DX1033]	MC9S08RG16MDWE@SOIC28 [DX1033]
MC9S08RG16MFD@QFN48 [DX4021]	MC9S08RG16MFDE@QFN48 [DX4021]
MC9S08RG16MFG@LQFP44 [DX3003]	MC9S08RG16MFGE@LQFP44 [DX3003]
MC9S08RG16MFJ@LQFP32 [DX3001]	MC9S08RG16MFJE@LQFP32 [DX3001]
MC9S08RG16MP	MC9S08RG16MPE
MC9S08RG16VDW@SOIC28 [DX1033]	MC9S08RG16VDWE@SOIC28 [DX1033]
MC9S08RG16VFD@QFN48 [DX4021]	MC9S08RG16VFDE@QFN48 [DX4021]
MC9S08RG16VFG@LQFP44 [DX3003]	MC9S08RG16VFGE@LQFP44 [DX3003]
MC9S08RG16VFJ@LQFP32 [DX3001]	MC9S08RG16VFJE@LQFP32 [DX3001]
MC9S08RG16VP	MC9S08RG16VPE
MC9S08RG32CDW@SOIC28 [DX1033]	MC9S08RG32CDWE@SOIC28 [DX1033]
MC9S08RG32CFD@QFN48 [DX4021]	MC9S08RG32CFDE@QFN48 [DX4021]

MC9S08RG32CFG@LQFP44 [DX3003]
MC9S08RG32CFJ@LQFP32 [DX3001]
MC9S08RG32CP
MC9S08RG32MDW@SOIC28 [DX1033]
MC9S08RG32MFD@QFN48 [DX4021]
MC9S08RG32MFG@LQFP44 [DX3003]
MC9S08RG32MFJ@LQFP32 [DX3001]
MC9S08RG32MP
MC9S08RG32VDW@SOIC28 [DX1033]
MC9S08RG32VFD@QFN48 [DX4021]
MC9S08RG32VFG@LQFP44 [DX3003]
MC9S08RG32VFJ@LQFP32 [DX3001]
MC9S08RG32VP
MC9S08RG60CDW@SOIC28 [DX1033]
MC9S08RG60CFD@QFN48 [DX4021]
MC9S08RG60CFG@LQFP44 [DX3003]
MC9S08RG60CFJ@LQFP32 [DX3001]
MC9S08RG60CP
MC9S08RG60MDW@SOIC28 [DX1033]
MC9S08RG60MFD@QFN48 [DX4021]
MC9S08RG60MFG@LQFP44 [DX3003]
MC9S08RG60MFJ@LQFP32 [DX3001]
MC9S08RG60MP
MC9S08RG60VDW@SOIC28 [DX1033]
MC9S08RG60VFD@QFN48 [DX4021]
MC9S08RG60VFG@LQFP44 [DX3003]
MC9S08RG60VFJ@LQFP32 [DX3001]
MC9S08RG60VP
MC9S08RG8CDW@SOIC28 [DX1033]
MC9S08RG8CFD@QFN48 [DX4021]
MC9S08RG8CFG@LQFP44 [DX3003]
MC9S08RG8CFJ@LQFP32 [DX3001]
MC9S08RG8CP
MC9S08RG8MDW@SOIC28 [DX1033]
MC9S08RG8MFD@QFN48 [DX4021]
MC9S08RG8MFG@LQFP44 [DX3003]
MC9S08RG8MFJ@LQFP32 [DX3001]
MC9S08RG8MP
MC9S08RG8VDW@SOIC28 [DX1033]
MC9S08RG8VFD@QFN48 [DX4021]
MC9S08RG8VFG@LQFP44 [DX3003]
MC9S08RG8VFJ@LQFP32 [DX3001]
MC9S08RG8VP
MC9S08SE4CRL [DX0001]
MC9S08SE4CWL [DX1033]
MC9S08SE4MTG [DX1001]
MC9S08SE4VRL [DX0001]
MC9S08SE4VWL [DX1033]
MC9S08RG32CFGE@LQFP44 [DX3003]
MC9S08RG32CFJE@LQFP32 [DX3001]
MC9S08RG32CPE
MC9S08RG32MDWE@SOIC28 [DX1033]
MC9S08RG32MFDE@QFN48 [DX4021]
MC9S08RG32MFGE@LQFP44 [DX3003]
MC9S08RG32MFJE@LQFP32 [DX3001]
MC9S08RG32MPE
MC9S08RG32VDWE@SOIC28 [DX1033]
MC9S08RG32VFDE@QFN48 [DX4021]
MC9S08RG32VFGE@LQFP44 [DX3003]
MC9S08RG32VFJE@LQFP32 [DX3001]
MC9S08RG32VPE
MC9S08RG60CDWE@SOIC28 [DX1033]
MC9S08RG60CFDE@QFN48 [DX4021]
MC9S08RG60CFGE@LQFP44 [DX3003]
MC9S08RG60CFJE@LQFP32 [DX3001]
MC9S08RG60CPE
MC9S08RG60MDWE@SOIC28 [DX1033]
MC9S08RG60MFDE@QFN48 [DX4021]
MC9S08RG60MFGE@LQFP44 [DX3003]
MC9S08RG60MFJE@LQFP32 [DX3001]
MC9S08RG60MPE
MC9S08RG60VDWE@SOIC28 [DX1033]
MC9S08RG60VFDE@QFN48 [DX4021]
MC9S08RG60VFGE@LQFP44 [DX3003]
MC9S08RG60VFJE@LQFP32 [DX3001]
MC9S08RG60VPE
MC9S08RG8CDWE@SOIC28 [DX1033]
MC9S08RG8CFDE@QFN48 [DX4021]
MC9S08RG8CFGE@LQFP44 [DX3003]
MC9S08RG8CFJE@LQFP32 [DX3001]
MC9S08RG8CPE
MC9S08RG8MDWE@SOIC28 [DX1033]
MC9S08RG8MFDE@QFN48 [DX4021]
MC9S08RG8MFGE@LQFP44 [DX3003]
MC9S08RG8MFJE@LQFP32 [DX3001]
MC9S08RG8MPE
MC9S08RG8VDWE@SOIC28 [DX1033]
MC9S08RG8VFDE@QFN48 [DX4021]
MC9S08RG8VFGE@LQFP44 [DX3003]
MC9S08RG8VFJE@LQFP32 [DX3001]
MC9S08RG8VPE
MC9S08SE4CTG [DX1001]
MC9S08SE4MRL [DX0001]
MC9S08SE4MWL [DX1033]
MC9S08SE4VTG [DX1001]
MC9S08SE8CRL [DX0001]

MC9S08SE8CTG [DX1001]	MC9S08SE8CWL [DX1033]
MC9S08SE8MRL [DX0001]	MC9S08SE8MTG [DX1001]
MC9S08SE8MWL [DX1033]	MC9S08SE8VRL [DX0001]
MC9S08SE8VTG [DX1001]	MC9S08SE8VWL [DX1033]
MC9S08SG16CTG@TSSOP16 [DX1000]	MC9S08SG16CTGE@TSSOP16 [DX1000]
MC9S08SG16CTJ@TSSOP20 [DX1000]	MC9S08SG16CTJE@TSSOP20 [DX1000]
MC9S08SG16CTL@TSSOP28 [DX1001]	MC9S08SG16CTLE@TSSOP28 [DX1001]
MC9S08SG16MTG@TSSOP16 [DX1000]	MC9S08SG16MTGE@TSSOP16 [DX1000]
MC9S08SG16MTJ@TSSOP20 [DX1000]	MC9S08SG16MTJE@TSSOP20 [DX1000]
MC9S08SG16MTL@TSSOP28 [DX1001]	MC9S08SG16MTLE@TSSOP28 [DX1001]
MC9S08SG16VTG@TSSOP16 [DX1000]	MC9S08SG16VTGE@TSSOP16 [DX1000]
MC9S08SG16VTJ@TSSOP20 [DX1000]	MC9S08SG16VTJE@TSSOP20 [DX1000]
MC9S08SG16VTL@TSSOP28 [DX1001]	MC9S08SG16VTLE@TSSOP28 [DX1001]
MC9S08SG32CTG@TSSOP16 [DX1000]	MC9S08SG32CTGE@TSSOP16 [DX1000]
MC9S08SG32CTJ@TSSOP20 [DX1000]	MC9S08SG32CTJE@TSSOP20 [DX1000]
MC9S08SG32CTL@TSSOP28 [DX1001]	MC9S08SG32CTLE@TSSOP28 [DX1001]
MC9S08SG32MTG@TSSOP16 [DX1000]	MC9S08SG32MTGE@TSSOP16 [DX1000]
MC9S08SG32MTJ@TSSOP20 [DX1000]	MC9S08SG32MTJE@TSSOP20 [DX1000]
MC9S08SG32MTL@TSSOP28 [DX1001]	MC9S08SG32MTLE@TSSOP28 [DX1001]
MC9S08SG32VTG@TSSOP16 [DX1000]	MC9S08SG32VTGE@TSSOP16 [DX1000]
MC9S08SG32VTJ@TSSOP20 [DX1000]	MC9S08SG32VTJE@TSSOP20 [DX1000]
MC9S08SG32VTL@TSSOP28 [DX1001]	MC9S08SG32VTLE@TSSOP28 [DX1001]
MC9S08SG4CSC@SOIC8 [DX1030]	MC9S08SG4CSCE@SOIC8 [DX1030]
MC9S08SG4CTG@TSSOP16 [DX1000]	MC9S08SG4CTGE@TSSOP16 [DX1000]
MC9S08SG4CTJ@TSSOP20 [DX1000]	MC9S08SG4CTJE@TSSOP20 [DX1000]
MC9S08SG4MSC@SOIC8 [DX1030]	MC9S08SG4MSCE@SOIC8 [DX1030]
MC9S08SG4MTG@TSSOP16 [DX1000]	MC9S08SG4MTGE@TSSOP16 [DX1000]
MC9S08SG4MTJ@TSSOP20 [DX1000]	MC9S08SG4MTJE@TSSOP20 [DX1000]
MC9S08SG4VSC@SOIC8 [DX1030]	MC9S08SG4VSCE@SOIC8 [DX1030]
MC9S08SG4VTG@TSSOP16 [DX1000]	MC9S08SG4VTGE@TSSOP16 [DX1000]
MC9S08SG4VTJ@TSSOP20 [DX1000]	MC9S08SG4VTJE@TSSOP20 [DX1000]
MC9S08SG8CSC@SOIC8 [DX1030]	MC9S08SG8CSCE@SOIC8 [DX1030]
MC9S08SG8CTG@TSSOP16 [DX1000]	MC9S08SG8CTGE@TSSOP16 [DX1000]
MC9S08SG8CTJ@TSSOP20 [DX1000]	MC9S08SG8CTJE@TSSOP20 [DX1000]
MC9S08SG8MSC@SOIC8 [DX1030]	MC9S08SG8MSCE@SOIC8 [DX1030]
MC9S08SG8MTG@TSSOP16 [DX1000]	MC9S08SG8MTGE@TSSOP16 [DX1000]
MC9S08SG8MTJ@TSSOP20 [DX1000]	MC9S08SG8MTJE@TSSOP20 [DX1000]
MC9S08SG8VSC@SOIC8 [DX1030]	MC9S08SG8VSCE@SOIC8 [DX1030]
MC9S08SG8VTG@TSSOP16 [DX1000]	MC9S08SG8VTGE@TSSOP16 [DX1000]
MC9S08SG8VTJ@TSSOP20 [DX1000]	MC9S08SG8VTJE@TSSOP20 [DX1000]
MC9S08SH16CTG@TSSOP16 [DX1000]	MC9S08SH16CTGE@TSSOP16 [DX1000]
MC9S08SH16CTJ@TSSOP20 [DX1000]	MC9S08SH16CTJE@TSSOP20 [DX1000]
MC9S08SH16CTL@TSSOP28 [DX1001]	MC9S08SH16CTLE@TSSOP28 [DX1001]
MC9S08SH16CWL@SOIC28 [DX1033]	MC9S08SH16CWLE@SOIC28 [DX1033]
MC9S08SH16MTG@TSSOP16 [DX1000]	MC9S08SH16MTGE@TSSOP16 [DX1000]
MC9S08SH16MTJ@TSSOP20 [DX1000]	MC9S08SH16MTJE@TSSOP20 [DX1000]
MC9S08SH16MTL@TSSOP28 [DX1001]	MC9S08SH16MTLE@TSSOP28 [DX1001]
MC9S08SH16MWL@SOIC28 [DX1033]	MC9S08SH16MWLE@SOIC28 [DX1033]

MC9S08SH16VTG@TSSOP16 [DX1000]　　MC9S08SH16VTGE@TSSOP16 [DX1000]
MC9S08SH16VTJ@TSSOP20 [DX1000]　　MC9S08SH16VTJE@TSSOP20 [DX1000]
MC9S08SH16VTL@TSSOP28 [DX1001]　　MC9S08SH16VTLE@TSSOP28 [DX1001]
MC9S08SH16VWL@SOIC28 [DX1033]　　MC9S08SH16VWLE@SOIC28 [DX1033]
MC9S08SH32CTG@TSSOP16 [DX1000]　　MC9S08SH32CTGE@TSSOP16 [DX1000]
MC9S08SH32CTJ@TSSOP20 [DX1000]　　MC9S08SH32CTJE@TSSOP20 [DX1000]
MC9S08SH32CTL@TSSOP28 [DX1001]　　MC9S08SH32CTLE@TSSOP28 [DX1001]
MC9S08SH32CWL@SOIC28 [DX1033]　　MC9S08SH32CWLE@SOIC28 [DX1033]
MC9S08SH32MTG@TSSOP16 [DX1000]　　MC9S08SH32MTGE@TSSOP16 [DX1000]
MC9S08SH32MTJ@TSSOP20 [DX1000]　　MC9S08SH32MTJE@TSSOP20 [DX1000]
MC9S08SH32MTL@TSSOP28 [DX1001]　　MC9S08SH32MTLE@TSSOP28 [DX1001]
MC9S08SH32MWL@SOIC28 [DX1033]　　MC9S08SH32MWLE@SOIC28 [DX1033]
MC9S08SH32VTG@TSSOP16 [DX1000]　　MC9S08SH32VTGE@TSSOP16 [DX1000]
MC9S08SH32VTJ@TSSOP20 [DX1000]　　MC9S08SH32VTJE@TSSOP20 [DX1000]
MC9S08SH32VTL@TSSOP28 [DX1001]　　MC9S08SH32VTLE@TSSOP28 [DX1001]
MC9S08SH32VWL@SOIC28 [DX1033]　　MC9S08SH32VWLE@SOIC28 [DX1033]
MC9S08SH4CFK@QFN24 [DX4012]
MC9S08SH4CFK@QFN24(auto trim) [DX4012]
MC9S08SH4CFKE@QFN24 [DX4012]
MC9S08SH4CFKE@QFN24(auto trim) [DX4012]
MC9S08SH4CPJ　　MC9S08SH4CPJ(auto trim)
MC9S08SH4CPJE　　MC9S08SH4CPJE(auto trim)
MC9S08SH4CSC@SOIC8 [DX1030]
MC9S08SH4CSC@SOIC8(auto trim) [DX1030]
MC9S08SH4CSCE@SOIC8 [DX1030]
MC9S08SH4CSCE@SOIC8(auto trim) [DX1030]
MC9S08SH4CTG@TSSOP16 [DX1000]
MC9S08SH4CTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4CTGE@TSSOP16 [DX1000]
MC9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4CTJ@TSSOP20 [DX1000]
MC9S08SH4CTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH4CTJE@TSSOP20 [DX1000]
MC9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4CWJ@SOIC20 [DX1033]
MC9S08SH4CWJ@SOIC20(auto trim) [DX1033]
MC9S08SH4CWJE@SOIC20 [DX1033]
MC9S08SH4CWJE@SOIC20(auto trim) [DX1033]
MC9S08SH4MFK@QFN24 [DX4012]
MC9S08SH4MFK@QFN24(auto trim) [DX4012]
MC9S08SH4MFKE@QFN24 [DX4012]
MC9S08SH4MFKE@QFN24(auto trim) [DX4012]
MC9S08SH4MPJ　　MC9S08SH4MPJ(auto trim)
MC9S08SH4MPJE　　MC9S08SH4MPJE(auto trim)
MC9S08SH4MSC@SOIC8 [DX1030]
MC9S08SH4MSC@SOIC8(auto trim) [DX1030]
MC9S08SH4MSCE@SOIC8 [DX1030]
MC9S08SH4MSCE@SOIC8(auto trim) [DX1030]

MC9S08SH4MTG@TSSOP16 [DX1000]
MC9S08SH4MTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4MTGE@TSSOP16 [DX1000]
MC9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4MTJ@TSSOP20 [DX1000]
MC9S08SH4MTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH4MTJE@TSSOP20 [DX1000]
MC9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4MWJ@SOIC20 [DX1033]
MC9S08SH4MWJ@SOIC20(auto trim) [DX1033]
MC9S08SH4MWJE@SOIC20 [DX1033]
MC9S08SH4MWJE@SOIC20(auto trim) [DX1033]
MC9S08SH4VFK@QFN24 [DX4012]
MC9S08SH4VFK@QFN24(auto trim) [DX4012]
MC9S08SH4VFKE@QFN24 [DX4012]
MC9S08SH4VFKE@QFN24(auto trim) [DX4012]
MC9S08SH4VPJ MC9S08SH4VPJ(auto trim)
MC9S08SH4VPJE MC9S08SH4VPJE(auto trim)
MC9S08SH4VSC@SOIC8 [DX1030]
MC9S08SH4VSC@SOIC8(auto trim) [DX1030]
MC9S08SH4VSCE@SOIC8 [DX1030]
MC9S08SH4VSCE@SOIC8(auto trim) [DX1030]
MC9S08SH4VTG@TSSOP16 [DX1000]
MC9S08SH4VTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4VTGE@TSSOP16 [DX1000]
MC9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4VTJ@TSSOP20 [DX1000]
MC9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH4VTJE@TSSOP20 [DX1000]
MC9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4VWJ@SOIC20 [DX1033]
MC9S08SH4VWJ@SOIC20(auto trim) [DX1033]
MC9S08SH4VWJE@SOIC20 [DX1033]
MC9S08SH4VWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8CFK@QFN24 [DX4012]
MC9S08SH8CFK@QFN24(auto trim) [DX4012]
MC9S08SH8CFKE@QFN24 [DX4012]
MC9S08SH8CFKE@QFN24(auto trim) [DX4012]
MC9S08SH8CPJ MC9S08SH8CPJ(auto trim)
MC9S08SH8CPJE MC9S08SH8CPJE(auto trim)
MC9S08SH8CSC@SOIC8 [DX1030]
MC9S08SH8CSC@SOIC8(auto trim) [DX1030]
MC9S08SH8CSCE@SOIC8 [DX1030]
MC9S08SH8CSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8CTG@TSSOP16 [DX1000]
MC9S08SH8CTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8CTGE@TSSOP16 [DX1000]
MC9S08SH8CTGE@TSSOP16(auto trim) [DX1000]

MC9S08SH8CTJ@TSSOP20 [DX1000]
MC9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8CTJE@TSSOP20 [DX1000]
MC9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH8CWJ@SOIC20 [DX1033]
MC9S08SH8CWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8CWJE@SOIC20 [DX1033]
MC9S08SH8CWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8MFK@QFN24 [DX4012]
MC9S08SH8MFK@QFN24(auto trim) [DX4012]
MC9S08SH8MFKE@QFN24 [DX4012]
MC9S08SH8MFKE@QFN24(auto trim) [DX4012]
MC9S08SH8MPJ MC9S08SH8MPJ(auto trim)
MC9S08SH8MPJE MC9S08SH8MPJE(auto trim)
MC9S08SH8MSC@SOIC8 [DX1030]
MC9S08SH8MSC@SOIC8(auto trim) [DX1030]
MC9S08SH8MSCE@SOIC8 [DX1030]
MC9S08SH8MSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8MTG@TSSOP16 [DX1000]
MC9S08SH8MTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8MTGE@TSSOP16 [DX1000]
MC9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH8MTJ@TSSOP20 [DX1000]
MC9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8MTJE@TSSOP20 [DX1000]
MC9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH8MWJ@SOIC20 [DX1033]
MC9S08SH8MWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8MWJE@SOIC20 [DX1033]
MC9S08SH8MWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8VFK@QFN24 [DX4012]
MC9S08SH8VFK@QFN24(auto trim) [DX4012]
MC9S08SH8VFKE@QFN24 [DX4012]
MC9S08SH8VFKE@QFN24(auto trim) [DX4012]
MC9S08SH8VPJ MC9S08SH8VPJ(auto trim)
MC9S08SH8VPJE MC9S08SH8VPJE(auto trim)
MC9S08SH8VSC@SOIC8 [DX1030]
MC9S08SH8VSC@SOIC8(auto trim) [DX1030]
MC9S08SH8VSCE@SOIC8 [DX1030]
MC9S08SH8VSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8VTG@TSSOP16 [DX1000]
MC9S08SH8VTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8VTGE@TSSOP16 [DX1000]
MC9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH8VTJ@TSSOP20 [DX1000]
MC9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8VTJE@TSSOP20 [DX1000]
MC9S08SH8VTJE@TSSOP20(auto trim) [DX1000]

MC9S08SH8VWJ@SOIC20 [DX1033]
MC9S08SH8VWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8VWJE@SOIC20 [DX1033]
MC9S08SH8VWJE@SOIC20(auto trim) [DX1033]
MC9S08SL16CTJ@TSSOP20 [DX1000]
MC9S08SL16CTJE@TSSOP20 [DX1000]
MC9S08SL16CTL@TSSOP28 [DX1001]
MC9S08SL16CTLE@TSSOP28 [DX1001]
MC9S08SL16MTJ@TSSOP20 [DX1000]
MC9S08SL16MTJE@TSSOP20 [DX1000]
MC9S08SL16MTL@TSSOP28 [DX1001]
MC9S08SL16MTLE@TSSOP28 [DX1001]
MC9S08SL16VTJ@TSSOP20 [DX1000]
MC9S08SL16VTJE@TSSOP20 [DX1000]
MC9S08SL16VTL@TSSOP28 [DX1001]
MC9S08SL16VTLE@TSSOP28 [DX1001]
MC9S08SL8CTJ@TSSOP20 [DX1000]
MC9S08SL8CTJE@TSSOP20 [DX1000]
MC9S08SL8CTL@TSSOP28 [DX1001]
MC9S08SL8CTLE@TSSOP28 [DX1001]
MC9S08SL8MTJ@TSSOP20 [DX1000]
MC9S08SL8MTJE@TSSOP20 [DX1000]
MC9S08SL8MTL@TSSOP28 [DX1001]
MC9S08SL8MTLE@TSSOP28 [DX1001]
MC9S08SL8VTJ@TSSOP20 [DX1000]
MC9S08SL8VTJE@TSSOP20 [DX1000]
MC9S08SL8VTL@TSSOP28 [DX1001]
MC9S08SL8VTLE@TSSOP28 [DX1001]
MC9S08SV16CBM@SDIP32 [DX0032]
MC9S08SV16CLC@LQFP32 [DX3001]
MC9S08SV16MBM@SDIP32 [DX0032]
MC9S08SV16MLC@LQFP32 [DX3001]
MC9S08SV16VBM@SDIP32 [DX0032]
MC9S08SV16VLC@LQFP32 [DX3001]
MC9S08SV8CBM@SDIP32 [DX0032]
MC9S08SV8CLC@LQFP32 [DX3001]
MC9S08SV8MBM@SDIP32 [DX0032]
MC9S08SV8MLC@LQFP32 [DX3001]
MC9S08SV8VBM@SDIP32 [DX0032]
MC9S08SV8VLC@LQFP32 [DX3001]
MC9S12A128BCFU@TQFP80 [DX3018]
MC9S12A128BCPV@TQFP112 [DX3026]
MC9S12A128BMFU@TQFP80 [DX3018]
MC9S12A128BMPV@TQFP112 [DX3026]
MC9S12A128BVFU@TQFP80 [DX3018]
MC9S12A128BVPV@TQFP112 [DX3026]
MC9S12A128CFU@TQFP80 [DX3018]
MC9S12A128CPV@TQFP112 [DX3026]
MC9S12A128MFU@TQFP80 [DX3018]
MC9S12A128MPV@TQFP112 [DX3026]
MC9S12A128VFU@TQFP80 [DX3018]
MC9S12A128VPV@TQFP112 [DX3026]
MC9S12A256BCFU@TQFP80 [DX3018]
MC9S12A256BCPV@TQFP112 [DX3026]
MC9S12A256BMFU@TQFP80 [DX3018]
MC9S12A256BMPV@TQFP112 [DX3026]
MC9S12A256BVFU@TQFP80 [DX3018]
MC9S12A256BVPV@TQFP112 [DX3026]
MC9S12A256CFU@TQFP80 [DX3018]
MC9S12A256CPV@TQFP112 [DX3026]
MC9S12A256MFU@TQFP80 [DX3018]
MC9S12A256MPV@TQFP112 [DX3026]
MC9S12A256VFU@TQFP80 [DX3018]
MC9S12A256VPV@TQFP112 [DX3026]
MC9S12A512CPV@TQFP112 [DX3026]
MC9S12A512MPV@TQFP112 [DX3026]
MC9S12A512VPV@TQFP112 [DX3026]
MC9S12A64CFU@TQFP80 [DX3018]
MC9S12A64CPV@TQFP112 [DX3026]
MC9S12A64MFU@TQFP80 [DX3018]
MC9S12A64MPV@TQFP112 [DX3026]
MC9S12A64VFU@TQFP80 [DX3018]
MC9S12A64VPV@TQFP112 [DX3026]
MC9S12B128CFU@TQFP80 [DX3018]
MC9S12B128CPV@TQFP112 [DX3026]
MC9S12B128MFU@TQFP80 [DX3018]
MC9S12B128MPV@TQFP112 [DX3026]
MC9S12B128VFU@TQFP80 [DX3018]
MC9S12B128VPV@TQFP112 [DX3026]
MC9S12B256CFU@TQFP80 [DX3018]
MC9S12B256CPV@TQFP112 [DX3026]
MC9S12B256MFU@TQFP80 [DX3018]
MC9S12B256MPV@TQFP112 [DX3026]
MC9S12B256VFU@TQFP80 [DX3018]
MC9S12B256VPV@TQFP112 [DX3026]
MC9S12B64CFU@TQFP80 [DX3018]
MC9S12B64CPV@TQFP112 [DX3026]
MC9S12B64MFU@TQFP80 [DX3018]
MC9S12B64MPV@TQFP112 [DX3026]
MC9S12B64VFU@TQFP80 [DX3018]
MC9S12B64VPV@TQFP112 [DX3026]
MC9S12C128CFA@TQFP48 [DX3007]

MC9S12C128CFU@TQFP80 [DX3018]
MC9S12C128CPB@TQFP52 [DX3010]
MC9S12C128MFA@TQFP48 [DX3007]
MC9S12C128MFU@TQFP80 [DX3018]
MC9S12C128MPB@TQFP52 [DX3010]
MC9S12C128VFA@TQFP48 [DX3007]
MC9S12C128VFU@TQFP80 [DX3018]
MC9S12C128VPB@TQFP52 [DX3010]
MC9S12C32CFA16@TQFP48 [DX3007]
MC9S12C32CFA25@TQFP48 [DX3007]
MC9S12C32CFU16@TQFP80 [DX3018]
MC9S12C32CFU25@TQFP80 [DX3018]
MC9S12C32CPB16@TQFP52 [DX3010]
MC9S12C32CPB25@TQFP52 [DX3010]
MC9S12C32MFA16@TQFP48 [DX3007]
MC9S12C32MFA25@TQFP48 [DX3007]
MC9S12C32MFU16@TQFP80 [DX3018]
MC9S12C32MFU25@TQFP80 [DX3018]
MC9S12C32MPB16@TQFP52 [DX3010]
MC9S12C32MPB25@TQFP52 [DX3010]
MC9S12C32VFA16@TQFP48 [DX3007]
MC9S12C32VFA25@TQFP48 [DX3007]
MC9S12C32VFU16@TQFP80 [DX3018]
MC9S12C32VFU25@TQFP80 [DX3018]
MC9S12C32VPB16@TQFP52 [DX3010]
MC9S12C32VPB25@TQFP52 [DX3010]
MC9S12C64CFA@TQFP48 [DX3007]
MC9S12C64CFU@TQFP80 [DX3018]
MC9S12C64CPB@TQFP52 [DX3010]
MC9S12C64MFA@TQFP48 [DX3007]
MC9S12C64MFU@TQFP80 [DX3018]
MC9S12C64MPB@TQFP52 [DX3010]
MC9S12C64VFA@TQFP48 [DX3007]
MC9S12C64VFU@TQFP80 [DX3018]
MC9S12C64VPB@TQFP52 [DX3010]
MC9S12C96CFA@TQFP48 [DX3007]
MC9S12C96CFU@TQFP80 [DX3018]
MC9S12C96CPB@TQFP52 [DX3010]
MC9S12C96MFA@TQFP48 [DX3007]
MC9S12C96MFU@TQFP80 [DX3018]
MC9S12C96MPB@TQFP52 [DX3010]
MC9S12C96VFA@TQFP48 [DX3007]
MC9S12C96VFU@TQFP80 [DX3018]
MC9S12C96VPB@TQFP52 [DX3010]
MC9S12D32CFU@TQFP80 [DX3018]
MC9S12D32MFU@TQFP80 [DX3018]
MC9S12D32VFU@TQFP80 [DX3018]
MC9S12D64CFU@TQFP80 [DX3018]
MC9S12D64CPV@TQFP112 [DX3026]
MC9S12D64MFU@TQFP80 [DX3018]
MC9S12D64MPV@TQFP112 [DX3026]
MC9S12D64VFU@TQFP80 [DX3018]
MC9S12D64VPV@TQFP112 [DX3026]
MC9S12DB128BCFU@TQFP80 [DX3018]
MC9S12DB128BCPV@TQFP112 [DX3026]
MC9S12DB128BMFU@TQFP80 [DX3018]
MC9S12DB128BMPV@TQFP112 [DX3026]
MC9S12DB128BVFU@TQFP80 [DX3018]
MC9S12DB128BVPV@TQFP112 [DX3026]
MC9S12DB128CFU@TQFP80 [DX3018]
MC9S12DB128CPV@TQFP112 [DX3026]
MC9S12DB128MFU@TQFP80 [DX3018]
MC9S12DB128MPV@TQFP112 [DX3026]
MC9S12DB128VFU@TQFP80 [DX3018]
MC9S12DB128VPV@TQFP112 [DX3026]
MC9S12DG128BCFU@TQFP80 [DX3018]
MC9S12DG128BCPV@TQFP112 [DX3026]
MC9S12DG128BMFU@TQFP80 [DX3018]
MC9S12DG128BMPV@TQFP112 [DX3026]
MC9S12DG128BVFU@TQFP80 [DX3018]
MC9S12DG128BVPV@TQFP112 [DX3026]
MC9S12DG128CFU@TQFP80 [DX3018]
MC9S12DG128CPV@TQFP112 [DX3026]
MC9S12DG128ECFU@TQFP80 [DX3018]
MC9S12DG128ECPV@TQFP112 [DX3026]
MC9S12DG128EMFU@TQFP80 [DX3018]
MC9S12DG128EMPV@TQFP112 [DX3026]
MC9S12DG128EVFU@TQFP80 [DX3018]
MC9S12DG128EVPV@TQFP112 [DX3026]
MC9S12DG128MFU@TQFP80 [DX3018]
MC9S12DG128MPV@TQFP112 [DX3026]
MC9S12DG128VFU@TQFP80 [DX3018]
MC9S12DG128VPV@TQFP112 [DX3026]
MC9S12DG256BCFU@TQFP80 [DX3018]
MC9S12DG256BCPV@TQFP112 [DX3026]
MC9S12DG256BMFU@TQFP80 [DX3018]
MC9S12DG256BMPV@TQFP112 [DX3026]
MC9S12DG256BVFU@TQFP80 [DX3018]
MC9S12DG256BVPV@TQFP112 [DX3026]
MC9S12DG256CCFU@TQFP80 [DX3018]
MC9S12DG256CCPV@TQFP112 [DX3026]
MC9S12DG256CFU@TQFP80 [DX3018]
MC9S12DG256CMFU@TQFP80 [DX3018]
MC9S12DG256CMPV@TQFP112 [DX3026]
MC9S12DG256CPV@TQFP112 [DX3026]
MC9S12DG256CVFU@TQFP80 [DX3018]

MC9S12DG256CVPV@TQFP112 [DX3026]
MC9S12DG256MPV@TQFP112 [DX3026]
MC9S12DG256VPV@TQFP112 [DX3026]
MC9S12DJ128BCPV@TQFP112 [DX3026]
MC9S12DJ128BMPV@TQFP112 [DX3026]
MC9S12DJ128BVPV@TQFP112 [DX3026]
MC9S12DJ128CPV@TQFP112 [DX3026]
MC9S12DJ128ECPV@TQFP112 [DX3026]
MC9S12DJ128EMPV@TQFP112 [DX3026]
MC9S12DJ128EVPV@TQFP112 [DX3026]
MC9S12DJ128MPV@TQFP112 [DX3026]
MC9S12DJ128VPV@TQFP112 [DX3026]
MC9S12DJ256BCPV@TQFP112 [DX3026]
MC9S12DJ256BMPV@TQFP112 [DX3026]
MC9S12DJ256BVPV@TQFP112 [DX3026]
MC9S12DJ256CCPV@TQFP112 [DX3026]
MC9S12DJ256CMFU@TQFP80 [DX3018]
MC9S12DJ256CPV@TQFP112 [DX3026]
MC9S12DJ256CVPV@TQFP112 [DX3026]
MC9S12DJ256MPV@TQFP112 [DX3026]
MC9S12DJ256VPV@TQFP112 [DX3026]
MC9S12DJ512MPV@TQFP112 [DX3026]
MC9S12DJ64CFU@TQFP80 [DX3018]
MC9S12DJ64MFU@TQFP80 [DX3018]
MC9S12DJ64VFU@TQFP80 [DX3018]
MC9S12DP256BCFU@TQFP80 [DX3018]
MC9S12DP256BMFU@TQFP80 [DX3018]
MC9S12DP256BVFU@TQFP80 [DX3018]
MC9S12DP256CCFU@TQFP80 [DX3018]
MC9S12DP256CMFU@TQFP80 [DX3018]
MC9S12DP256CVFU@TQFP80 [DX3018]
MC9S12DP512CPV@TQFP112 [DX3026]
MC9S12DP512VPV@TQFP112 [DX3026]
MC9S12DT128BCPV@TQFP112 [DX3026]
MC9S12DT128BMPV@TQFP112 [DX3026]
MC9S12DT128BVPV@TQFP112 [DX3026]
MC9S12DT128CPV@TQFP112 [DX3026]
MC9S12DT128ECPV@TQFP112 [DX3026]
MC9S12DT128EMPV@TQFP112 [DX3026]
MC9S12DT128EVPV@TQFP112 [DX3026]
MC9S12DT128MPV@TQFP112 [DX3026]
MC9S12DT128VPV@TQFP112 [DX3026]
MC9S12DT256BCPV@TQFP112 [DX3026]
MC9S12DT256BMPV@TQFP112 [DX3026]
MC9S12DT256BVPV@TQFP112 [DX3026]
MC9S12DT256CCPV@TQFP112 [DX3026]
MC9S12DT256CMFU@TQFP80 [DX3018]
MC9S12DT256CPV@TQFP112 [DX3026]
MC9S12DG256MFU@TQFP80 [DX3018]
MC9S12DG256VFU@TQFP80 [DX3018]
MC9S12DJ128BCFU@TQFP80 [DX3018]
MC9S12DJ128BMFU@TQFP80 [DX3018]
MC9S12DJ128BVFU@TQFP80 [DX3018]
MC9S12DJ128CFU@TQFP80 [DX3018]
MC9S12DJ128ECFU@TQFP80 [DX3018]
MC9S12DJ128EMFU@TQFP80 [DX3018]
MC9S12DJ128EVFU@TQFP80 [DX3018]
MC9S12DJ128MFU@TQFP80 [DX3018]
MC9S12DJ128VFU@TQFP80 [DX3018]
MC9S12DJ256BCFU@TQFP80 [DX3018]
MC9S12DJ256BMFU@TQFP80 [DX3018]
MC9S12DJ256BVFU@TQFP80 [DX3018]
MC9S12DJ256CCFU@TQFP80 [DX3018]
MC9S12DJ256CFU@TQFP80 [DX3018]
MC9S12DJ256CMPV@TQFP112 [DX3026]
MC9S12DJ256CVFU@TQFP80 [DX3018]
MC9S12DJ256MFU@TQFP80 [DX3018]
MC9S12DJ256VFU@TQFP80 [DX3018]
MC9S12DJ512CPV@TQFP112 [DX3026]
MC9S12DJ512VPV@TQFP112 [DX3026]
MC9S12DJ64CPV@TQFP112 [DX3026]
MC9S12DJ64MPV@TQFP112 [DX3026]
MC9S12DJ64VPV@TQFP112 [DX3026]
MC9S12DP256BCPV@TQFP112 [DX3026]
MC9S12DP256BMPV@TQFP112 [DX3026]
MC9S12DP256BVPV@TQFP112 [DX3026]
MC9S12DP256CCPV@TQFP112 [DX3026]
MC9S12DP256CMPV@TQFP112 [DX3026]
MC9S12DP256CVPV@TQFP112 [DX3026]
MC9S12DP512MPV@TQFP112 [DX3026]
MC9S12DT128BCFU@TQFP80 [DX3018]
MC9S12DT128BMFU@TQFP80 [DX3018]
MC9S12DT128BVFU@TQFP80 [DX3018]
MC9S12DT128CFU@TQFP80 [DX3018]
MC9S12DT128ECFU@TQFP80 [DX3018]
MC9S12DT128EMFU@TQFP80 [DX3018]
MC9S12DT128EVFU@TQFP80 [DX3018]
MC9S12DT128MFU@TQFP80 [DX3018]
MC9S12DT128VFU@TQFP80 [DX3018]
MC9S12DT256BCFU@TQFP80 [DX3018]
MC9S12DT256BMFU@TQFP80 [DX3018]
MC9S12DT256BVFU@TQFP80 [DX3018]
MC9S12DT256CCFU@TQFP80 [DX3018]
MC9S12DT256CFU@TQFP80 [DX3018]
MC9S12DT256CMPV@TQFP112 [DX3026]
MC9S12DT256CVFU@TQFP80 [DX3018]

MC9S12DT256CVPV@TQFP112 [DX3026]
MC9S12DT256MFU@TQFP80 [DX3018]
MC9S12DT256MPV@TQFP112 [DX3026]
MC9S12DT256VFU@TQFP80 [DX3018]
MC9S12DT256VPV@TQFP112 [DX3026]
MC9S12DT512CPV@TQFP112 [DX3026]
MC9S12DT512MPV@TQFP112 [DX3026]
MC9S12DT512VPV@TQFP112 [DX3026]
MC9S12E128CFU@TQFP80 [DX3018]
MC9S12E128CFUE@TQFP80 [DX3018]
MC9S12E128CPV@TQFP112 [DX3026]
MC9S12E128CPVE@TQFP112 [DX3026]
MC9S12E128MFU@TQFP80 [DX3018]
MC9S12E128MFUE@TQFP80 [DX3018]
MC9S12E128MPV@TQFP112 [DX3026]
MC9S12E128MPVE@TQFP112 [DX3026]
MC9S12E128VFU@TQFP80 [DX3018]
MC9S12E128VFUE@TQFP80 [DX3018]
MC9S12E128VPV@TQFP112 [DX3026]
MC9S12E128VPVE@TQFP112 [DX3026]
MC9S12E256CFU@TQFP80 [DX3018]
MC9S12E256CFUE@TQFP80 [DX3018]
MC9S12E256CPV@TQFP112 [DX3026]
MC9S12E256CPVE@TQFP112 [DX3026]
MC9S12E256MFU@TQFP80 [DX3018]
MC9S12E256MFUE@TQFP80 [DX3018]
MC9S12E256MPV@TQFP112 [DX3026]
MC9S12E256MPVE@TQFP112 [DX3026]
MC9S12E256VFU@TQFP80 [DX3018]
MC9S12E256VFUE@TQFP80 [DX3018]
MC9S12E256VPV@TQFP112 [DX3026]
MC9S12E256VPVE@TQFP112 [DX3026]
MC9S12E32CFC@TQFP64 [DX4023]
MC9S12E32CFCE@TQFP64 [DX4023]
MC9S12E32CFU@TQFP80 [DX3018]
MC9S12E32CFUE@TQFP80 [DX3018]
MC9S12E32MFC@TQFP64 [DX4023]
MC9S12E32MFCE@TQFP64 [DX4023]
MC9S12E32MFU@TQFP80 [DX3018]
MC9S12E32MFUE@TQFP80 [DX3018]
MC9S12E32VFC@TQFP64 [DX4023]
MC9S12E32VFCE@TQFP64 [DX4023]
MC9S12E32VFU@TQFP80 [DX3018]
MC9S12E32VFUE@TQFP80 [DX3018]
MC9S12E64CFU@TQFP80 [DX3018]
MC9S12E64CFUE@TQFP80 [DX3018]
MC9S12E64CPV@TQFP112 [DX3026]
MC9S12E64CPVE@TQFP112 [DX3026]
MC9S12E64MFU@TQFP80 [DX3018]
MC9S12E64MFUE@TQFP80 [DX3018]
MC9S12E64MPV@TQFP112 [DX3026]
MC9S12E64MPVE@TQFP112 [DX3026]
MC9S12E64VFU@TQFP80 [DX3018]
MC9S12E64VFUE@TQFP80 [DX3018]
MC9S12E64VPV@TQFP112 [DX3026]
MC9S12E64VPVE@TQFP112 [DX3026]
MC9S12GC128CFA@TQFP48 [DX3007]
MC9S12GC128CFU@TQFP80 [DX3018]
MC9S12GC128CPB@TQFP52 [DX3010]
MC9S12GC128MFA@TQFP48 [DX3007]
MC9S12GC128MFU@TQFP80 [DX3018]
MC9S12GC128MPB@TQFP52 [DX3010]
MC9S12GC128VFA@TQFP48 [DX3007]
MC9S12GC128VFU@TQFP80 [DX3018]
MC9S12GC128VPB@TQFP52 [DX3010]
MC9S12GC16CFA@TQFP48 [DX3007]
MC9S12GC16CFU@TQFP80 [DX3018]
MC9S12GC16CPB@TQFP52 [DX3010]
MC9S12GC16MFA@TQFP48 [DX3007]
MC9S12GC16MFU@TQFP80 [DX3018]
MC9S12GC16MPB@TQFP52 [DX3010]
MC9S12GC16VFA@TQFP48 [DX3007]
MC9S12GC16VFU@TQFP80 [DX3018]
MC9S12GC16VPB@TQFP52 [DX3010]
MC9S12GC32CFA@TQFP48 [DX3007]
MC9S12GC32CFU@TQFP80 [DX3018]
MC9S12GC32CPB@TQFP52 [DX3010]
MC9S12GC32MFA@TQFP48 [DX3007]
MC9S12GC32MFU@TQFP80 [DX3018]
MC9S12GC32MPB@TQFP52 [DX3010]
MC9S12GC32VFA@TQFP48 [DX3007]
MC9S12GC32VFU@TQFP80 [DX3018]
MC9S12GC32VPB@TQFP52 [DX3010]
MC9S12GC64CFA@TQFP48 [DX3007]
MC9S12GC64CFU@TQFP80 [DX3018]
MC9S12GC64CPB@TQFP52 [DX3010]
MC9S12GC64MFA@TQFP48 [DX3007]
MC9S12GC64MFU@TQFP80 [DX3018]
MC9S12GC64MPB@TQFP52 [DX3010]
MC9S12GC64VFA@TQFP48 [DX3007]
MC9S12GC64VFU@TQFP80 [DX3018]
MC9S12GC64VPB@TQFP52 [DX3010]
MC9S12GC96CFA@TQFP48 [DX3007]
MC9S12GC96CFU@TQFP80 [DX3018]
MC9S12GC96CPB@TQFP52 [DX3010]
MC9S12GC96MFA@TQFP48 [DX3007]

MC9S12GC96MFU@TQFP80 [DX3018]
MC9S12GC96MPB@TQFP52 [DX3010]
MC9S12GC96VFA@TQFP48 [DX3007]
MC9S12GC96VFU@TQFP80 [DX3018]
MC9S12GC96VPB@TQFP52 [DX3010]
MC9S12H128CFV@QFP144 [DX3035]
MC9S12H128CFVE@QFP144 [DX3035]
MC9S12H128CPV@QFP112 [DX3026]
MC9S12H128CPVE@QFP112 [DX3026]
MC9S12H128MFV@QFP144 [DX3035]
MC9S12H128MFVE@QFP144 [DX3035]
MC9S12H128MPV@QFP112 [DX3026]
MC9S12H128MPVE@QFP112 [DX3026]
MC9S12H128VFV@QFP144 [DX3035]
MC9S12H128VFVE@QFP144 [DX3035]
MC9S12H128VPV@QFP112 [DX3026]
MC9S12H128VPVE@QFP112 [DX3026]
MC9S12H256CFV@QFP144 [DX3035]
MC9S12H256CFVE@QFP144 [DX3035]
MC9S12H256CPV@QFP112 [DX3026]
MC9S12H256CPVE@QFP112 [DX3026]
MC9S12H256MFV@QFP144 [DX3035]
MC9S12H256MFVE@QFP144 [DX3035]
MC9S12H256MPV@QFP112 [DX3026]
MC9S12H256MPVE@QFP112 [DX3026]
MC9S12H256VFV@QFP144 [DX3035]
MC9S12H256VFVE@QFP144 [DX3035]
MC9S12H256VPV@QFP112 [DX3026]
MC9S12H256VPVE@QFP112 [DX3026]
MC9S12HA32CLH@QFP64 [DX3011]
MC9S12HA32CLHE@QFP64 [DX3011]
MC9S12HA32CLL@QFP100 [DX3043]
MC9S12HA32CLLE@QFP100 [DX3043]
MC9S12HA32MLH@QFP64 [DX3011]
MC9S12HA32MLHE@QFP64 [DX3011]
MC9S12HA32MLL@QFP100 [DX3043]
MC9S12HA32MLLE@QFP100 [DX3043]
MC9S12HA32VLH@QFP64 [DX3011]
MC9S12HA32VLHE@QFP64 [DX3011]
MC9S12HA32VLL@QFP100 [DX3043]
MC9S12HA32VLLE@QFP100 [DX3043]
MC9S12HA48CLH@QFP64 [DX3011]
MC9S12HA48CLHE@QFP64 [DX3011]
MC9S12HA48CLL@QFP100 [DX3043]
MC9S12HA48CLLE@QFP100 [DX3043]
MC9S12HA48MLH@QFP64 [DX3011]
MC9S12HA48MLHE@QFP64 [DX3011]
MC9S12HA48MLL@QFP100 [DX3043]
MC9S12HA48MLLE@QFP100 [DX3043]
MC9S12HA48VLH@QFP64 [DX3011]
MC9S12HA48VLHE@QFP64 [DX3011]
MC9S12HA48VLL@QFP100 [DX3043]
MC9S12HA48VLLE@QFP100 [DX3043]
MC9S12HA64CLH@QFP64 [DX3011]
MC9S12HA64CLHE@QFP64 [DX3011]
MC9S12HA64CLL@QFP100 [DX3043]
MC9S12HA64CLLE@QFP100 [DX3043]
MC9S12HA64MLH@QFP64 [DX3011]
MC9S12HA64MLHE@QFP64 [DX3011]
MC9S12HA64MLL@QFP100 [DX3043]
MC9S12HA64MLLE@QFP100 [DX3043]
MC9S12HA64VLH@QFP64 [DX3011]
MC9S12HA64VLHE@QFP64 [DX3011]
MC9S12HA64VLL@QFP100 [DX3043]
MC9S12HA64VLLE@QFP100 [DX3043]
MC9S12HN64CAA@TQFP80 [DX3018]
MC9S12HN64CAL@LQFP112 [DX3026]
MC9S12HN64CFU@TQFP80 [DX3018]
MC9S12HN64CPV@LQFP112 [DX3026]
MC9S12HN64MAA@TQFP80 [DX3018]
MC9S12HN64MAL@LQFP112 [DX3026]
MC9S12HN64MFU@TQFP80 [DX3018]
MC9S12HN64MPV@LQFP112 [DX3026]
MC9S12HN64VAA@TQFP80 [DX3018]
MC9S12HN64VAL@LQFP112 [DX3026]
MC9S12HN64VFU@TQFP80 [DX3018]
MC9S12HN64VPV@LQFP112 [DX3026]
MC9S12HY32CLH@QFP64 [DX3011]
MC9S12HY32CLHE@QFP64 [DX3011]
MC9S12HY32CLL@QFP100 [DX3043]
MC9S12HY32CLLE@QFP100 [DX3043]
MC9S12HY32MLH@QFP64 [DX3011]
MC9S12HY32MLHE@QFP64 [DX3011]
MC9S12HY32MLL@QFP100 [DX3043]
MC9S12HY32MLLE@QFP100 [DX3043]
MC9S12HY32VLH@QFP64 [DX3011]
MC9S12HY32VLHE@QFP64 [DX3011]
MC9S12HY32VLL@QFP100 [DX3043]
MC9S12HY32VLLE@QFP100 [DX3043]
MC9S12HY48CLH@QFP64 [DX3011]
MC9S12HY48CLHE@QFP64 [DX3011]
MC9S12HY48CLL@QFP100 [DX3043]
MC9S12HY48CLLE@QFP100 [DX3043]
MC9S12HY48MLH@QFP64 [DX3011]
MC9S12HY48MLHE@QFP64 [DX3011]
MC9S12HY48MLL@QFP100 [DX3043]

MC9S12HY48MLLE@QFP100 [DX3043]
MC9S12HY48VLHE@QFP64 [DX3011]
MC9S12HY48VLLE@QFP100 [DX3043]
MC9S12HY64CLHE@QFP64 [DX3011]
MC9S12HY64CLLE@QFP100 [DX3043]
MC9S12HY64MLHE@QFP64 [DX3011]
MC9S12HY64MLLE@QFP100 [DX3043]
MC9S12HY64VLHE@QFP64 [DX3011]
MC9S12HY64VLLE@QFP100 [DX3043]
MC9S12HZ128CAL@LQFP112 [DX3026]
MC9S12HZ128CPV@LQFP112 [DX3026]
MC9S12HZ128MAL@LQFP112 [DX3026]
MC9S12HZ128MPV@LQFP112 [DX3026]
MC9S12HZ128VAL@LQFP112 [DX3026]
MC9S12HZ128VPV@LQFP112 [DX3026]
MC9S12HZ256CAL@LQFP112 [DX3026]
MC9S12HZ256CPV@LQFP112 [DX3026]
MC9S12HZ256MAL@LQFP112 [DX3026]
MC9S12HZ256MPV@LQFP112 [DX3026]
MC9S12HZ256VAL@LQFP112 [DX3026]
MC9S12HZ256VPV@LQFP112 [DX3026]
MC9S12HZ64CAL@LQFP112 [DX3026]
MC9S12HZ64CPV@LQFP112 [DX3026]
MC9S12HZ64MAL@LQFP112 [DX3026]
MC9S12HZ64MPV@LQFP112 [DX3026]
MC9S12HZ64VAL@LQFP112 [DX3026]
MC9S12HZ64VPV@LQFP112 [DX3026]
MC9S12KG256CPV@LQFP112 [DX3026]
MC9S12KG256MPV@LQFP112 [DX3026]
MC9S12KG256VPV@LQFP112 [DX3026]
MC9S12KT256MPV@LQFP112 [DX3026]
MC9S12NE64CPV@LQFP112 [DX3026]
MC9S12NE64VTU@TQFP80 [DX3017]
MC9S12P128CFT@QFN48 [DX4021]
MC9S12P128CQK@QFP80 [DX3018]
MC9S12P128MLH@QFP64 [DX3011]
MC9S12P128VFT@QFN48 [DX4021]
MC9S12P128VQK@QFP80 [DX3018]
MC9S12P32CLH@QFP64 [DX3011]
MC9S12P32MFT@QFN48 [DX4021]
MC9S12P32MQK@QFP80 [DX3018]
MC9S12P32VLH@QFP64 [DX3011]
MC9S12P64CFT@QFN48 [DX4021]
MC9S12P64CQK@QFP80 [DX3018]
MC9S12P64MLH@QFP64 [DX3011]
MC9S12P64VFT@QFN48 [DX4021]
MC9S12P64VQK@QFP80 [DX3018]
MC9S12P96CLH@QFP64 [DX3011]
MC9S12HY48VLH@QFP64 [DX3011]
MC9S12HY48VLL@QFP100 [DX3043]
MC9S12HY64CLH@QFP64 [DX3011]
MC9S12HY64CLL@QFP100 [DX3043]
MC9S12HY64MLH@QFP64 [DX3011]
MC9S12HY64MLL@QFP100 [DX3043]
MC9S12HY64VLH@QFP64 [DX3011]
MC9S12HY64VLL@QFP100 [DX3043]
MC9S12HZ128CAA@TQFP80 [DX3018]
MC9S12HZ128CFU@TQFP80 [DX3018]
MC9S12HZ128MAA@TQFP80 [DX3018]
MC9S12HZ128MFU@TQFP80 [DX3018]
MC9S12HZ128VAA@TQFP80 [DX3018]
MC9S12HZ128VFU@TQFP80 [DX3018]
MC9S12HZ256CAA@TQFP80 [DX3018]
MC9S12HZ256CFU@TQFP80 [DX3018]
MC9S12HZ256MAA@TQFP80 [DX3018]
MC9S12HZ256MFU@TQFP80 [DX3018]
MC9S12HZ256VAA@TQFP80 [DX3018]
MC9S12HZ256VFU@TQFP80 [DX3018]
MC9S12HZ64CAA@TQFP80 [DX3018]
MC9S12HZ64CFU@TQFP80 [DX3018]
MC9S12HZ64MAA@TQFP80 [DX3018]
MC9S12HZ64MFU@TQFP80 [DX3018]
MC9S12HZ64VAA@TQFP80 [DX3018]
MC9S12HZ64VFU@TQFP80 [DX3018]
MC9S12KG256CFU@TQFP80 [DX3018]
MC9S12KG256MFU@TQFP80 [DX3018]
MC9S12KG256VFU@TQFP80 [DX3018]
MC9S12KT256CPV@LQFP112 [DX3026]
MC9S12KT256VPV@LQFP112 [DX3026]
MC9S12NE64CPVE@LQFP112 [DX3026]
MC9S12NE64VTUE@TQFP80 [DX3017]
MC9S12P128CLH@QFP64 [DX3011]
MC9S12P128MFT@QFN48 [DX4021]
MC9S12P128MQK@QFP80 [DX3018]
MC9S12P128VLH@QFP64 [DX3011]
MC9S12P32CFT@QFN48 [DX4021]
MC9S12P32CQK@QFP80 [DX3018]
MC9S12P32MLH@QFP64 [DX3011]
MC9S12P32VFT@QFN48 [DX4021]
MC9S12P32VQK@QFP80 [DX3018]
MC9S12P64CLH@QFP64 [DX3011]
MC9S12P64MFT@QFN48 [DX4021]
MC9S12P64MQK@QFP80 [DX3018]
MC9S12P64VLH@QFP64 [DX3011]
MC9S12P96CFT@QFN48 [DX4021]
MC9S12P96CQK@QFP80 [DX3018]

MC9S12P96MFT@QFN48 [DX4021]
MC9S12P96MLH@QFP64 [DX3011]
MC9S12P96MQK@QFP80 [DX3018]
MC9S12P96VFT@QFN48 [DX4021]
MC9S12P96VLH@QFP64 [DX3011]
MC9S12P96VQK@QFP80 [DX3018]
MC9S12Q128CFA@TQFP48 [DX3007]
MC9S12Q128CFAE@TQFP48 [DX3007]
MC9S12Q128CFU@TQFP80 [DX3018]
MC9S12Q128CFUE@TQFP80 [DX3018]
MC9S12Q128CPB@TQFP52 [DX3010]
MC9S12Q128CPBE@TQFP52 [DX3010]
MC9S12Q128MFA@TQFP48 [DX3007]
MC9S12Q128MFAE@TQFP48 [DX3007]
MC9S12Q128MFU@TQFP80 [DX3018]
MC9S12Q128MFUE@TQFP80 [DX3018]
MC9S12Q128MPB@TQFP52 [DX3010]
MC9S12Q128MPBE@TQFP52 [DX3010]
MC9S12Q128VFA@TQFP48 [DX3007]
MC9S12Q128VFAE@TQFP48 [DX3007]
MC9S12Q128VFU@TQFP80 [DX3018]
MC9S12Q128VFUE@TQFP80 [DX3018]
MC9S12Q128VPB@TQFP52 [DX3010]
MC9S12Q128VPBE@TQFP52 [DX3010]
MC9S12Q32CFA@TQFP48 [DX3007]
MC9S12Q32CFAE@TQFP48 [DX3007]
MC9S12Q32CFU@TQFP80 [DX3018]
MC9S12Q32CFUE@TQFP80 [DX3018]
MC9S12Q32CPB@TQFP52 [DX3010]
MC9S12Q32CPBE@TQFP52 [DX3010]
MC9S12Q32MFA@TQFP48 [DX3007]
MC9S12Q32MFAE@TQFP48 [DX3007]
MC9S12Q32MFU@TQFP80 [DX3018]
MC9S12Q32MFUE@TQFP80 [DX3018]
MC9S12Q32MPB@TQFP52 [DX3010]
MC9S12Q32MPBE@TQFP52 [DX3010]
MC9S12Q32VFA@TQFP48 [DX3007]
MC9S12Q32VFAE@TQFP48 [DX3007]
MC9S12Q32VFU@TQFP80 [DX3018]
MC9S12Q32VFUE@TQFP80 [DX3018]
MC9S12Q32VPB@TQFP52 [DX3010]
MC9S12Q32VPBE@TQFP52 [DX3010]
MC9S12Q64CFA@TQFP48 [DX3007]
MC9S12Q64CFAE@TQFP48 [DX3007]
MC9S12Q64CFU@TQFP80 [DX3018]
MC9S12Q64CFUE@TQFP80 [DX3018]
MC9S12Q64CPB@TQFP52 [DX3010]
MC9S12Q64CPBE@TQFP52 [DX3010]
MC9S12Q64MFA@TQFP48 [DX3007]
MC9S12Q64MFAE@TQFP48 [DX3007]
MC9S12Q64MFU@TQFP80 [DX3018]
MC9S12Q64MFUE@TQFP80 [DX3018]
MC9S12Q64MPB@TQFP52 [DX3010]
MC9S12Q64MPBE@TQFP52 [DX3010]
MC9S12Q64VFA@TQFP48 [DX3007]
MC9S12Q64VFAE@TQFP48 [DX3007]
MC9S12Q64VFU@TQFP80 [DX3018]
MC9S12Q64VFUE@TQFP80 [DX3018]
MC9S12Q64VPB@TQFP52 [DX3010]
MC9S12Q64VPBE@TQFP52 [DX3010]
MC9S12Q96CFA@TQFP48 [DX3007]
MC9S12Q96CFAE@TQFP48 [DX3007]
MC9S12Q96CFU@TQFP80 [DX3018]
MC9S12Q96CFUE@TQFP80 [DX3018]
MC9S12Q96CPB@TQFP52 [DX3010]
MC9S12Q96CPBE@TQFP52 [DX3010]
MC9S12Q96MFA@TQFP48 [DX3007]
MC9S12Q96MFAE@TQFP48 [DX3007]
MC9S12Q96MFU@TQFP80 [DX3018]
MC9S12Q96MFUE@TQFP80 [DX3018]
MC9S12Q96MPB@TQFP52 [DX3010]
MC9S12Q96MPBE@TQFP52 [DX3010]
MC9S12Q96VFA@TQFP48 [DX3007]
MC9S12Q96VFAE@TQFP48 [DX3007]
MC9S12Q96VFU@TQFP80 [DX3018]
MC9S12Q96VFUE@TQFP80 [DX3018]
MC9S12Q96VPB@TQFP52 [DX3010]
MC9S12Q96VPBE@TQFP52 [DX3010]
MC9S12T64CPK16@TQFP80 [DX3016]
MC9S12T64MPK16@TQFP80 [DX3016]
MC9S12T64VPK16@TQFP80 [DX3016]
MC9S12UF32PB@QFP64 [DX3011]
MC9S12UF32PBE@QFP64 [DX3011]
MC9S12UF32PU@QFP100 [DX3021]
MC9S12UF32PUE@QFP100 [DX3021]
MC9S12XA128CAA@TQFP80 [DX3018]
MC9S12XA128CAL@TQFP112 [DX3026]
MC9S12XA128CFU@TQFP80 [DX3018]
MC9S12XA128CPV@TQFP112 [DX3026]
MC9S12XA128MAA@TQFP80 [DX3018]
MC9S12XA128MAL@TQFP112 [DX3026]
MC9S12XA128MFU@TQFP80 [DX3018]
MC9S12XA128MPV@TQFP112 [DX3026]
MC9S12XA128VAA@TQFP80 [DX3018]
MC9S12XA128VAL@TQFP112 [DX3026]
MC9S12XA128VFU@TQFP80 [DX3018]

MC9S12XA128VPV@TQFP112 [DX3026]
MC9S12XA256CAA@TQFP80 [DX3018]
MC9S12XA256CAG@LQFP144 [DX3035]
MC9S12XA256CAL@TQFP112 [DX3026]
MC9S12XA256CFU@TQFP80 [DX3018]
MC9S12XA256CFV@LQFP144 [DX3035]
MC9S12XA256CPV@TQFP112 [DX3026]
MC9S12XA256MAA@TQFP80 [DX3018]
MC9S12XA256MAG@LQFP144 [DX3035]
MC9S12XA256MAL@TQFP112 [DX3026]
MC9S12XA256MFU@TQFP80 [DX3018]
MC9S12XA256MFV@LQFP144 [DX3035]
MC9S12XA256MPV@TQFP112 [DX3026]
MC9S12XA256VAA@TQFP80 [DX3018]
MC9S12XA256VAG@LQFP144 [DX3035]
MC9S12XA256VAL@TQFP112 [DX3026]
MC9S12XA256VFU@TQFP80 [DX3018]
MC9S12XA256VFV@LQFP144 [DX3035]
MC9S12XA256VPV@TQFP112 [DX3026]
MC9S12XA512CAA@TQFP80 [DX3018]
MC9S12XA512CAG@LQFP144 [DX3035]
MC9S12XA512CAL@TQFP112 [DX3026]
MC9S12XA512CFU@TQFP80 [DX3018]
MC9S12XA512CFV@LQFP144 [DX3035]
MC9S12XA512CPV@TQFP112 [DX3026]
MC9S12XA512MAA@TQFP80 [DX3018]
MC9S12XA512MAG@LQFP144 [DX3035]
MC9S12XA512MAL@TQFP112 [DX3026]
MC9S12XA512MFU@TQFP80 [DX3018]
MC9S12XA512MFV@LQFP144 [DX3035]
MC9S12XA512MPV@TQFP112 [DX3026]
MC9S12XA512VAA@TQFP80 [DX3018]
MC9S12XA512VAG@LQFP144 [DX3035]
MC9S12XA512VAL@TQFP112 [DX3026]
MC9S12XA512VFU@TQFP80 [DX3018]
MC9S12XA512VFV@LQFP144 [DX3035]
MC9S12XA512VPV@TQFP112 [DX3026]
MC9S12XB128CAA@TQFP80 [DX3018]
MC9S12XB128CAL@TQFP112 [DX3026]
MC9S12XB128CFU@TQFP80 [DX3018]
MC9S12XB128CPV@TQFP112 [DX3026]
MC9S12XB128MAA@TQFP80 [DX3018]
MC9S12XB128MAL@TQFP112 [DX3026]
MC9S12XB128MFU@TQFP80 [DX3018]
MC9S12XB128MPV@TQFP112 [DX3026]
MC9S12XB128VAA@TQFP80 [DX3018]
MC9S12XB128VAL@TQFP112 [DX3026]
MC9S12XB128VFU@TQFP80 [DX3018]
MC9S12XB128VPV@TQFP112 [DX3026]
MC9S12XB256CAA@TQFP80 [DX3018]
MC9S12XB256CAL@TQFP112 [DX3026]
MC9S12XB256CFU@TQFP80 [DX3018]
MC9S12XB256CPV@TQFP112 [DX3026]
MC9S12XB256MAA@TQFP80 [DX3018]
MC9S12XB256MAL@TQFP112 [DX3026]
MC9S12XB256MFU@TQFP80 [DX3018]
MC9S12XB256MPV@TQFP112 [DX3026]
MC9S12XB256VAA@TQFP80 [DX3018]
MC9S12XB256VAL@TQFP112 [DX3026]
MC9S12XB256VFU@TQFP80 [DX3018]
MC9S12XB256VPV@TQFP112 [DX3026]
MC9S12XD128CAA@TQFP80 [DX3018]
MC9S12XD128CAL@TQFP112 [DX3026]
MC9S12XD128CFU@TQFP80 [DX3018]
MC9S12XD128CPV@TQFP112 [DX3026]
MC9S12XD128MAA@TQFP80 [DX3018]
MC9S12XD128MAL@TQFP112 [DX3026]
MC9S12XD128MFU@TQFP80 [DX3018]
MC9S12XD128MPV@TQFP112 [DX3026]
MC9S12XD128VAA@TQFP80 [DX3018]
MC9S12XD128VAL@TQFP112 [DX3026]
MC9S12XD128VFU@TQFP80 [DX3018]
MC9S12XD128VPV@TQFP112 [DX3026]
MC9S12XD256CAA@TQFP80 [DX3018]
MC9S12XD256CAG@LQFP144 [DX3035]
MC9S12XD256CAL@TQFP112 [DX3026]
MC9S12XD256CFU@TQFP80 [DX3018]
MC9S12XD256CFV@LQFP144 [DX3035]
MC9S12XD256CPV@TQFP112 [DX3026]
MC9S12XD256MAA@TQFP80 [DX3018]
MC9S12XD256MAG@LQFP144 [DX3035]
MC9S12XD256MAL@TQFP112 [DX3026]
MC9S12XD256MFU@TQFP80 [DX3018]
MC9S12XD256MFV@LQFP144 [DX3035]
MC9S12XD256MPV@TQFP112 [DX3026]
MC9S12XD256VAA@TQFP80 [DX3018]
MC9S12XD256VAG@LQFP144 [DX3035]
MC9S12XD256VAL@TQFP112 [DX3026]
MC9S12XD256VFU@TQFP80 [DX3018]
MC9S12XD256VFV@LQFP144 [DX3035]
MC9S12XD256VPV@TQFP112 [DX3026]
MC9S12XD64CAA@TQFP80 [DX3018]
MC9S12XD64CFU@TQFP80 [DX3018]
MC9S12XD64MAA@TQFP80 [DX3018]
MC9S12XD64MFU@TQFP80 [DX3018]
MC9S12XD64VAA@TQFP80 [DX3018]

MC9S12XD64VFU@TQFP80 [DX3018]
MC9S12XDG128CAA@TQFP80 [DX3018]
MC9S12XDG128CAL@TQFP112 [DX3026]
MC9S12XDG128CFU@TQFP80 [DX3018]
MC9S12XDG128CPV@TQFP112 [DX3026]
MC9S12XDG128MAA@TQFP80 [DX3018]
MC9S12XDG128MAL@TQFP112 [DX3026]
MC9S12XDG128MFU@TQFP80 [DX3018]
MC9S12XDG128MPV@TQFP112 [DX3026]
MC9S12XDG128VAA@TQFP80 [DX3018]
MC9S12XDG128VAL@TQFP112 [DX3026]
MC9S12XDG128VFU@TQFP80 [DX3018]
MC9S12XDG128VPV@TQFP112 [DX3026]
MC9S12XDP512CAA@TQFP80 [DX3018]
MC9S12XDP512CAG@LQFP144 [DX3035]
MC9S12XDP512CAL@TQFP112 [DX3026]
MC9S12XDP512CFU@TQFP80 [DX3018]
MC9S12XDP512CFV@LQFP144 [DX3035]
MC9S12XDP512CPV@TQFP112 [DX3026]
MC9S12XDP512MAA@TQFP80 [DX3018]
MC9S12XDP512MAG@LQFP144 [DX3035]
MC9S12XDP512MAL@TQFP112 [DX3026]
MC9S12XDP512MFU@TQFP80 [DX3018]
MC9S12XDP512MFV@LQFP144 [DX3035]
MC9S12XDP512MPV@TQFP112 [DX3026]
MC9S12XDP512VAA@TQFP80 [DX3018]
MC9S12XDP512VAG@LQFP144 [DX3035]
MC9S12XDP512VAL@TQFP112 [DX3026]
MC9S12XDP512VFU@TQFP80 [DX3018]
MC9S12XDP512VFV@LQFP144 [DX3035]
MC9S12XDP512VPV@TQFP112 [DX3026]
MC9S12XDQ256CAA@TQFP80 [DX3018]
MC9S12XDQ256CAG@LQFP144 [DX3035]
MC9S12XDQ256CAL@TQFP112 [DX3026]
MC9S12XDQ256CFU@TQFP80 [DX3018]
MC9S12XDQ256CFV@LQFP144 [DX3035]
MC9S12XDQ256CPV@TQFP112 [DX3026]
MC9S12XDQ256MAA@TQFP80 [DX3018]
MC9S12XDQ256MAG@LQFP144 [DX3035]
MC9S12XDQ256MAL@TQFP112 [DX3026]
MC9S12XDQ256MFU@TQFP80 [DX3018]
MC9S12XDQ256MFV@LQFP144 [DX3035]
MC9S12XDQ256MPV@TQFP112 [DX3026]
MC9S12XDQ256VAA@TQFP80 [DX3018]
MC9S12XDQ256VAG@LQFP144 [DX3035]
MC9S12XDQ256VAL@TQFP112 [DX3026]
MC9S12XDQ256VFU@TQFP80 [DX3018]
MC9S12XDQ256VFV@LQFP144 [DX3035]
MC9S12XDQ256VPV@TQFP112 [DX3026]
MC9S12XDT256CAA@TQFP80 [DX3018]
MC9S12XDT256CAG@LQFP144 [DX3035]
MC9S12XDT256CAL@TQFP112 [DX3026]
MC9S12XDT256CFU@TQFP80 [DX3018]
MC9S12XDT256CFV@LQFP144 [DX3035]
MC9S12XDT256CPV@TQFP112 [DX3026]
MC9S12XDT256MAA@TQFP80 [DX3018]
MC9S12XDT256MAG@LQFP144 [DX3035]
MC9S12XDT256MAL@TQFP112 [DX3026]
MC9S12XDT256MFU@TQFP80 [DX3018]
MC9S12XDT256MFV@LQFP144 [DX3035]
MC9S12XDT256MPV@TQFP112 [DX3026]
MC9S12XDT256VAA@TQFP80 [DX3018]
MC9S12XDT256VAG@LQFP144 [DX3035]
MC9S12XDT256VAL@TQFP112 [DX3026]
MC9S12XDT256VFU@TQFP80 [DX3018]
MC9S12XDT256VFV@LQFP144 [DX3035]
MC9S12XDT256VPV@TQFP112 [DX3026]
MC9S12XDT384CAA@TQFP80 [DX3018]
MC9S12XDT384CAG@LQFP144 [DX3035]
MC9S12XDT384CAL@TQFP112 [DX3026]
MC9S12XDT384CFV@LQFP144 [DX3035]
MC9S12XDT384CPU@TQFP80 [DX3018]
MC9S12XDT384CPV@TQFP112 [DX3026]
MC9S12XDT384MAA@TQFP80 [DX3018]
MC9S12XDT384MAG@LQFP144 [DX3035]
MC9S12XDT384MAL@TQFP112 [DX3026]
MC9S12XDT384MFV@LQFP144 [DX3035]
MC9S12XDT384MPU@TQFP80 [DX3018]
MC9S12XDT384MPV@TQFP112 [DX3026]
MC9S12XDT384VAA@TQFP80 [DX3018]
MC9S12XDT384VAG@LQFP144 [DX3035]
MC9S12XDT384VAL@TQFP112 [DX3026]
MC9S12XDT384VFV@LQFP144 [DX3035]
MC9S12XDT384VPU@TQFP80 [DX3018]
MC9S12XDT384VPV@TQFP112 [DX3026]
MC9S12XDT512CAA@TQFP80 [DX3018]
MC9S12XDT512CAG@LQFP144 [DX3035]
MC9S12XDT512CAL@TQFP112 [DX3026]
MC9S12XDT512CFU@TQFP80 [DX3018]
MC9S12XDT512CFV@LQFP144 [DX3035]
MC9S12XDT512CPV@TQFP112 [DX3026]
MC9S12XDT512MAA@TQFP80 [DX3018]
MC9S12XDT512MAG@LQFP144 [DX3035]
MC9S12XDT512MAL@TQFP112 [DX3026]
MC9S12XDT512MFU@TQFP80 [DX3018]
MC9S12XDT512MFV@LQFP144 [DX3035]

MC9S12XDT512MPV@TQFP112 [DX3026]
MC9S12XDT512VAA@TQFP80 [DX3018]
MC9S12XDT512VAG@LQFP144 [DX3035]
MC9S12XDT512VAL@TQFP112 [DX3026]
MC9S12XDT512VFU@TQFP80 [DX3018]
MC9S12XDT512VFV@LQFP144 [DX3035]
MC9S12XDT512VPV@TQFP112 [DX3026]
MC9S12XEA128CAA@TQFP80 [DX3018]
MC9S12XEA128CAL@TQFP112 [DX3026]
MC9S12XEA128MAA@TQFP80 [DX3018]
MC9S12XEA128MAL@TQFP112 [DX3026]
MC9S12XEA128VAA@TQFP80 [DX3018]
MC9S12XEA128VAL@TQFP112 [DX3026]
MC9S12XEA256CAA@TQFP80 [DX3018]
MC9S12XEA256CAG@LQFP144 [DX3035]
MC9S12XEA256CAL@TQFP112 [DX3026]
MC9S12XEA256MAA@TQFP80 [DX3018]
MC9S12XEA256MAG@LQFP144 [DX3035]
MC9S12XEA256MAL@TQFP112 [DX3026]
MC9S12XEA256VAA@TQFP80 [DX3018]
MC9S12XEA256VAG@LQFP144 [DX3035]
MC9S12XEA256VAL@TQFP112 [DX3026]
MC9S12XEG128CAA@TQFP80 [DX3018]
MC9S12XEG128CAL@TQFP112 [DX3026]
MC9S12XEG128MAA@TQFP80 [DX3018]
MC9S12XEG128MAL@TQFP112 [DX3026]
MC9S12XEG128VAA@TQFP80 [DX3018]
MC9S12XEG128VAL@TQFP112 [DX3026]
MC9S12XEG256CAA@QFP80 [DX3018]
MC9S12XEG256CAL@TQFP112 [DX3026]
MC9S12XEG256MAA@QFP80 [DX3018]
MC9S12XEG256MAL@TQFP112 [DX3026]
MC9S12XEG256VAA@QFP80 [DX3018]
MC9S12XEG256VAL@TQFP112 [DX3026]
MC9S12XEG384CAA@TQFP80 [DX3018]
MC9S12XEG384CAG@LQFP144 [DX3035]
MC9S12XEG384CAL@TQFP112 [DX3026]
MC9S12XEG384MAA@TQFP80 [DX3018]
MC9S12XEG384MAG@LQFP144 [DX3035]
MC9S12XEG384MAL@TQFP112 [DX3026]
MC9S12XEG384VAA@TQFP80 [DX3018]
MC9S12XEG384VAG@LQFP144 [DX3035]
MC9S12XEG384VAL@TQFP112 [DX3026]
MC9S12XEP100CAG@LQFP144 [DX3035]
MC9S12XEP100CAL@TQFP112 [DX3026]
MC9S12XEP100MAG@LQFP144 [DX3035]
MC9S12XEP100MAL@TQFP112 [DX3026]
MC9S12XEP100VAG@LQFP144 [DX3035]
MC9S12XEP100VAL@TQFP112 [DX3026]
MC9S12XEP768CAG@LQFP144 [DX3035]
MC9S12XEP768CAL@TQFP112 [DX3026]
MC9S12XEP768MAG@LQFP144 [DX3035]
MC9S12XEP768MAL@TQFP112 [DX3026]
MC9S12XEP768VAG@LQFP144 [DX3035]
MC9S12XEP768VAL@TQFP112 [DX3026]
MC9S12XEQ384CAA@TQFP80 [DX3018]
MC9S12XEQ384CAG@LQFP144 [DX3035]
MC9S12XEQ384CAL@TQFP112 [DX3026]
MC9S12XEQ384MAA@TQFP80 [DX3018]
MC9S12XEQ384MAG@LQFP144 [DX3035]
MC9S12XEQ384MAL@TQFP112 [DX3026]
MC9S12XEQ384VAA@TQFP80 [DX3018]
MC9S12XEQ384VAG@LQFP144 [DX3035]
MC9S12XEQ384VAL@TQFP112 [DX3026]
MC9S12XEQ512CAA@TQFP80 [DX3018]
MC9S12XEQ512CAG@LQFP144 [DX3035]
MC9S12XEQ512CAL@TQFP112 [DX3026]
MC9S12XEQ512MAA@TQFP80 [DX3018]
MC9S12XEQ512MAG@LQFP144 [DX3035]
MC9S12XEQ512MAL@TQFP112 [DX3026]
MC9S12XEQ512VAA@TQFP80 [DX3018]
MC9S12XEQ512VAG@LQFP144 [DX3035]
MC9S12XEQ512VAL@TQFP112 [DX3026]
MC9S12XET256CAA@TQFP80 [DX3018]
MC9S12XET256CAG@LQFP144 [DX3035]
MC9S12XET256CAL@TQFP112 [DX3026]
MC9S12XET256MAA@TQFP80 [DX3018]
MC9S12XET256MAG@LQFP144 [DX3035]
MC9S12XET256MAL@TQFP112 [DX3026]
MC9S12XET256VAA@TQFP80 [DX3018]
MC9S12XET256VAG@LQFP144 [DX3035]
MC9S12XET256VAL@TQFP112 [DX3026]
MC9S12XF128CAG@QFP144 [DX3035]
MC9S12XF128CAL@QFP112 [DX3026]
MC9S12XF128CLH@QFP64 [DX3011]
MC9S12XF128MAG@QFP144 [DX3035]
MC9S12XF128MAL@QFP112 [DX3026]
MC9S12XF128MLH@QFP64 [DX3011]
MC9S12XF128VAG@QFP144 [DX3035]
MC9S12XF128VAL@QFP112 [DX3026]
MC9S12XF128VLH@QFP64 [DX3011]
MC9S12XF256CAG@QFP144 [DX3035]
MC9S12XF256CAL@QFP112 [DX3026]
MC9S12XF256CLH@QFP64 [DX3011]
MC9S12XF256MAG@QFP144 [DX3035]
MC9S12XF256MAL@QFP112 [DX3026]

MC9S12XF256MLH@QFP64 [DX3011]
MC9S12XF256VAG@QFP144 [DX3035]
MC9S12XF256VAL@QFP112 [DX3026]
MC9S12XF256VLH@QFP64 [DX3011]
MC9S12XF384CAG@QFP144 [DX3035]
MC9S12XF384CAL@QFP112 [DX3026]
MC9S12XF384CLH@QFP64 [DX3011]
MC9S12XF384MAG@QFP144 [DX3035]
MC9S12XF384MAL@QFP112 [DX3026]
MC9S12XF384MLH@QFP64 [DX3011]
MC9S12XF384VAG@QFP144 [DX3035]
MC9S12XF384VAL@QFP112 [DX3026]
MC9S12XF384VLH@QFP64 [DX3011]
MC9S12XF512CAG@QFP144 [DX3035]
MC9S12XF512CAL@QFP112 [DX3026]
MC9S12XF512CLH@QFP64 [DX3011]
MC9S12XF512MAG@QFP144 [DX3035]
MC9S12XF512MAL@QFP112 [DX3026]
MC9S12XF512MLH@QFP64 [DX3011]
MC9S12XF512VAG@QFP144 [DX3035]
MC9S12XF512VAL@QFP112 [DX3026]
MC9S12XF512VLH@QFP64 [DX3011]
MC9S12XHY128CLL [DX3021]
MC9S12XHY128CLM [DX3026]
MC9S12XHY128MLL [DX3021]
MC9S12XHY128MLM [DX3026]
MC9S12XHY128VLL [DX3021]
MC9S12XHY128VLM [DX3026]
MC9S12XHY256CLL [DX3021]
MC9S12XHY256CLM [DX3026]
MC9S12XHY256MLL [DX3021]
MC9S12XHY256MLM [DX3026]
MC9S12XHY256VLL [DX3021]
MC9S12XHY256VLM [DX3026]
MC9S12XHZ256CAG@LQFP144 [DX3035]
MC9S12XHZ256CAL@TQFP112 [DX3026]
MC9S12XHZ256MAG@LQFP144 [DX3035]
MC9S12XHZ256MAL@TQFP112 [DX3026]
MC9S12XHZ256VAG@LQFP144 [DX3035]
MC9S12XHZ256VAL@TQFP112 [DX3026]
MC9S12XHZ384CAG@LQFP144 [DX3035]
MC9S12XHZ384CAL@TQFP112 [DX3026]
MC9S12XHZ384MAG@LQFP144 [DX3035]
MC9S12XHZ384MAL@TQFP112 [DX3026]
MC9S12XHZ384VAG@LQFP144 [DX3035]
MC9S12XHZ384VAL@TQFP112 [DX3026]
MC9S12XHZ512CAG@LQFP144 [DX3035]
MC9S12XHZ512CAL@TQFP112 [DX3026]
MC9S12XHZ512MAG@LQFP144 [DX3035]
MC9S12XHZ512MAL@TQFP112 [DX3026]
MC9S12XHZ512VAG@LQFP144 [DX3035]
MC9S12XHZ512VAL@TQFP112 [DX3026]
MC9S12XS128CAA@QFP80 [DX3018]
MC9S12XS128CAE@QFP64 [DX3011]
MC9S12XS128CAL@QFP112 [DX3026]
MC9S12XS128MAA@QFP80 [DX3018]
MC9S12XS128MAE@QFP64 [DX3011]
MC9S12XS128MAL@QFP112 [DX3026]
MC9S12XS128VAA@QFP80 [DX3018]
MC9S12XS128VAE@QFP64 [DX3011]
MC9S12XS128VAL@QFP112 [DX3026]
MC9S12XS256CAA@QFP80 [DX3018]
MC9S12XS256CAE@QFP64 [DX3011]
MC9S12XS256CAL@QFP112 [DX3026]
MC9S12XS256MAA@QFP80 [DX3018]
MC9S12XS256MAE@QFP64 [DX3011]
MC9S12XS256MAL@QFP112 [DX3026]
MC9S12XS256VAA@QFP80 [DX3018]
MC9S12XS256VAE@QFP64 [DX3011]
MC9S12XS256VAL@QFP112 [DX3026]
MC9S12XS64CAA@QFP80 [DX3018]
MC9S12XS64CAE@QFP64 [DX3011]
MC9S12XS64CAL@QFP112 [DX3026]
MC9S12XS64MAA@QFP80 [DX3018]
MC9S12XS64MAE@QFP64 [DX3011]
MC9S12XS64MAL@QFP112 [DX3026]
MC9S12XS64VAA@QFP80 [DX3018]
MC9S12XS64VAE@QFP64 [DX3011]
MC9S12XS64VAL@QFP112 [DX3026]
MCF51AC128ACFUE@QFP64 [DX3014]
MCF51AC128ACLKE@LQFP80 [DX3017]
MCF51AC128ACPUE@LQFP64 [DX3011]
MCF51AC128AMFUE@QFP64 [DX3014]
MCF51AC128AMLKE@LQFP80 [DX3017]
MCF51AC128AMPUE@LQFP64 [DX3011]
MCF51AC128AVFUE@QFP64 [DX3014]
MCF51AC128AVLKE@LQFP80 [DX3017]
MCF51AC128AVPUE@LQFP64 [DX3011]
MCF51AC128BCFUE@QFP64 [DX3014]
MCF51AC128BCLKE@LQFP80 [DX3017]
MCF51AC128BCPUE@LQFP64 [DX3011]
MCF51AC128BMFUE@QFP64 [DX3014]
MCF51AC128BMLKE@LQFP80 [DX3017]
MCF51AC128BMPUE@LQFP64 [DX3011]
MCF51AC128BVFUE@QFP64 [DX3014]
MCF51AC128BVLKE@LQFP80 [DX3017]

MCF51AC128BVPUE@LQFP64 [DX3011]
MCF51AC128CCFUE@QFP64 [DX3014]
MCF51AC128CCLKE@LQFP80 [DX3017]
MCF51AC128CCPUE@LQFP64 [DX3011]
MCF51AC128CMFUE@QFP64 [DX3014]
MCF51AC128CMLKE@LQFP80 [DX3017]
MCF51AC128CMPUE@LQFP64 [DX3011]
MCF51AC128CVFUE@QFP64 [DX3014]
MCF51AC128CVLKE@LQFP80 [DX3017]
MCF51AC128CVPUE@LQFP64 [DX3011]
MCF51AC256ACFUE@QFP64 [DX3014]
MCF51AC256ACLKE@LQFP80 [DX3017]
MCF51AC256ACPUE@LQFP64 [DX3011]
MCF51AC256AMFUE@QFP64 [DX3014]
MCF51AC256AMLKE@LQFP80 [DX3017]
MCF51AC256AMPUE@LQFP64 [DX3011]
MCF51AC256AVFUE@QFP64 [DX3014]
MCF51AC256AVLKE@LQFP80 [DX3017]
MCF51AC256AVPUE@LQFP64 [DX3011]
MCF51AC256BCFUE@QFP64 [DX3014]
MCF51AC256BCLKE@LQFP80 [DX3017]
MCF51AC256BCPUE@LQFP64 [DX3011]
MCF51AC256BMFUE@QFP64 [DX3014]
MCF51AC256BMLKE@LQFP80 [DX3017]
MCF51AC256BMPUE@LQFP64 [DX3011]
MCF51AC256BVFUE@QFP64 [DX3014]
MCF51AC256BVLKE@LQFP80 [DX3017]
MCF51AC256BVPUE@LQFP64 [DX3011]
MCF51AC256CCFUE@QFP64 [DX3014]
MCF51AC256CCLKE@LQFP80 [DX3017]
MCF51AC256CCPUE@LQFP64 [DX3011]
MCF51AC256CMFUE@QFP64 [DX3014]
MCF51AC256CMLKE@LQFP80 [DX3017]
MCF51AC256CMPUE@LQFP64 [DX3011]
MCF51AC256CVFUE@QFP64 [DX3014]
MCF51AC256CVLKE@LQFP80 [DX3017]
MCF51AC256CVPUE@LQFP64 [DX3011]
MCF51CN128CGT@QFN48 [DX4021]
MCF51CN128CLH@LQFP64 [DX3011]
MCF51CN128CLK@LQFP80 [DX3017]
MCF51CN128MGT@QFN48 [DX4021]
MCF51CN128MLH@LQFP64 [DX3011]
MCF51CN128MLK@LQFP80 [DX3017]
MCF51CN128VGT@QFN48 [DX4021]
MCF51CN128VLH@LQFP64 [DX3011]
MCF51CN128VLK@LQFP80 [DX3017]
MCF51JE128CLK@QFP80 [DX3016]
MCF51JE128CLL@QFP100 [DX3021]
MCF51JE128MLK@QFP80 [DX3016]
MCF51JE128MLL@QFP100 [DX3021]
MCF51JE128VLK@QFP80 [DX3016]
MCF51JE128VLL@QFP100 [DX3021]
MCF51JE256CLK@QFP80 [DX3016]
MCF51JE256CLL@QFP100 [DX3021]
MCF51JE256MLK@QFP80 [DX3016]
MCF51JE256MLL@QFP100 [DX3021]
MCF51JE256VLK@QFP80 [DX3016]
MCF51JE256VLL@QFP100 [DX3021]
MCF51JF128VLH@QFP64 [DX3011]
MCF51JM128CLD@LQFP44 [DX3005]
MCF51JM128CLH@LQFP64 [DX3011]
MCF51JM128CLK@LQFP80 [DX3017]
MCF51JM128CQH@QFP64 [DX3014]
MCF51JM128ECLK@LQFP80 [DX3017]
MCF51JM128EMLK@LQFP80 [DX3017]
MCF51JM128EVLK@LQFP80 [DX3017]
MCF51JM128MLD@LQFP44 [DX3005]
MCF51JM128MLH@LQFP64 [DX3011]
MCF51JM128MLK@LQFP80 [DX3017]
MCF51JM128MQH@QFP64 [DX3014]
MCF51JM128VLD@LQFP44 [DX3005]
MCF51JM128VLH@LQFP64 [DX3011]
MCF51JM128VLK@LQFP80 [DX3017]
MCF51JM128VQH@QFP64 [DX3014]
MCF51JM32CLD@LQFP44 [DX3005]
MCF51JM32CLH@LQFP64 [DX3011]
MCF51JM32CLK@LQFP80 [DX3017]
MCF51JM32CQH@QFP64 [DX3014]
MCF51JM32ECLK@LQFP80 [DX3017]
MCF51JM32EMLK@LQFP80 [DX3017]
MCF51JM32EVLK@LQFP80 [DX3017]
MCF51JM32MLD@LQFP44 [DX3005]
MCF51JM32MLH@LQFP64 [DX3011]
MCF51JM32MLK@LQFP80 [DX3017]
MCF51JM32MQH@QFP64 [DX3014]
MCF51JM32VLD@LQFP44 [DX3005]
MCF51JM32VLH@LQFP64 [DX3011]
MCF51JM32VLK@LQFP80 [DX3017]
MCF51JM32VQH@QFP64 [DX3014]
MCF51JM64CLD@LQFP44 [DX3005]
MCF51JM64CLH@LQFP64 [DX3011]
MCF51JM64CLK@LQFP80 [DX3017]
MCF51JM64CQH@QFP64 [DX3014]
MCF51JM64ECLK@LQFP80 [DX3017]
MCF51JM64EMLK@LQFP80 [DX3017]
MCF51JM64EVLK@LQFP80 [DX3017]

MCF51JM64MLD@LQFP44 [DX3005]
MCF51JM64MLH@LQFP64 [DX3011]
MCF51JM64MLK@LQFP80 [DX3017]
MCF51JM64MQH@QFP64 [DX3014]
MCF51JM64VLD@LQFP44 [DX3005]
MCF51JM64VLH@LQFP64 [DX3011]
MCF51JM64VLK@LQFP80 [DX3017]
MCF51JM64VQH@QFP64 [DX3014]
MCF51JU128VLH@QFP64 [DX3011]
MCF51QE128CLH@QFP64 [DX3011]
MCF51QE128CLK@QFP80 [DX3017]
MCF51QE128LH@QFP64 [DX3011]
MCF51QE128LK@QFP80 [DX3017]
MCF51QE128MLH@QFP64 [DX3011]
MCF51QE128MLK@QFP80 [DX3017]
MCF51QE128VLH@QFP64 [DX3011]
MCF51QE128VLK@QFP80 [DX3017]
MCF51QE32CLH@QFP64 [DX3011]
MCF51QE32CLK@QFP80 [DX3017]
MCF51QE32LH@QFP64 [DX3011]
MCF51QE32LK@QFP80 [DX3017]
MCF51QE32MLH@QFP64 [DX3011]
MCF51QE32MLK@QFP80 [DX3017]
MCF51QE32VLH@QFP64 [DX3011]
MCF51QE32VLK@QFP80 [DX3017]
MCF51QE64CLH@QFP64 [DX3011]
MCF51QE64CLK@QFP80 [DX3017]
MCF51QE64LH@QFP64 [DX3011]
MCF51QE64LK@QFP80 [DX3017]
MCF51QE64MLH@QFP64 [DX3011]
MCF51QE64MLK@QFP80 [DX3017]
MCF51QE64VLH@QFP64 [DX3011]
MCF51QE64VLK@QFP80 [DX3017]
MCF51QE96CLH@QFP64 [DX3011]
MCF51QE96CLK@QFP80 [DX3017]
MCF51QE96LH@QFP64 [DX3011]
MCF51QE96LK@QFP80 [DX3017]
MCF51QE96MLH@QFP64 [DX3011]
MCF51QE96MLK@QFP80 [DX3017]
MCF51QE96VLH@QFP64 [DX3011]
MCF51QE96VLK@QFP80 [DX3017]
MCF51QM128VLH@QFP64 [DX3011]
MCF52100CAE66@QFP64 [DX3011]
MCF52100CAE80@QFP64 [DX3011]
MCF52100CEP66@QFN64 [DX4023]
MCF52100CEP80@QFN64 [DX4023]
MCF52100LCVM66@BGA81 [DX5089]
MCF52100LCVM80@BGA81 [DX5089]
MCF52110CAE66@QFP64 [DX3011]
MCF52110CAE80@QFP64 [DX3011]
MCF52110CAF66@QFP100 [DX3021]
MCF52110CAF80@QFP100 [DX3021]
MCF52110CEP66@QFN64 [DX4023]
MCF52110CEP80@QFN64 [DX4023]
MCF52110LCVM66@BGA81 [DX5089]
MCF52110LCVM80@BGA81 [DX5089]
MCF5211CAE66@QFP64 [DX3011]
MCF5211CEP66@QFN64 [DX4023]
MCF5211LCVM66@BGA81 [DX5089]
MCF5211LCVM80@BGA81 [DX5089]
MCF5212CAE66@QFP64 [DX3011]
MCF5212LCVM66@BGA81 [DX5089]
MCF5212LCVM80@BGA81 [DX5089]
MCF5213CAF66@QFP100 [DX3021]
MCF5213CAF80@QFP100 [DX3021]
MCF5213LCVM66@BGA81 [DX5089]
MCF5213LCVM80@BGA81 [DX5089]
MCF52210CAE66@QFP64 [DX3011]
MCF52210CEP66@QFN64 [DX4023]
MCF52210CVM66@BGA81 [DX5089]
MCF52210CVM80@BGA81 [DX5089]
MCF52211CAE66@QFP64 [DX3011]
MCF52211CAF80@QFP100 [DX3021]
MCF52211CEP66@QFN64 [DX4023]
MCF52211CVM66@BGA81 [DX5089]
MCF52211CVM80@BGA81 [DX5089]
MCF52212AE50@QFP64 [DX3011]
MCF52212CAE50@QFP64 [DX3011]
MCF52213AE50@QFP64 [DX3011]
MCF52213CAE50@QFP64 [DX3011]
MCF52221CAE66@QFP64 [DX3011]
MCF52221CAE80@QFP64 [DX3011]
MCF52221CVM66@BGA81 [DX5089]
MCF52221CVM80@BGA81 [DX5089]
MCF52223CAF66@QFP100 [DX3021]
MCF52223CAF80@QFP100 [DX3021]
MCF52223CVM66@BGA81 [DX5089]
MCF52223CVM80@BGA81 [DX5089]
MCF52230CAF60@QFP80 [DX3018]
MCF52230CAL60@QFP112 [DX3026]
MCF52231CAF60@QFP80 [DX3018]
MCF52231CAL60@QFP112 [DX3026]
MCF52232AF50@QFP80 [DX3018]
MCF52232CAF50@QFP80 [DX3018]
MCF52233CAF60@QFP80 [DX3018]
MCF52233CAL60@QFP112 [DX3026]

MCF52234CAL60@QFP112 [DX3026]
MCF52234CVM60@BGA121 [DX5090]
MCF52235CAL60@QFP112 [DX3026]
MCF52235CVM60@BGA121 [DX5090]
MCF52236AF50@QFP80 [DX3018]
MCF52236CAF50@QFP80 [DX3018]
MCF52252AF80@QFP100 [DX3021]
MCF52252CAF66@QFP100 [DX3021]
MCF52254AF80@QFP100 [DX3021]
MCF52254CAF66@QFP100 [DX3021]
MCF52255CAF80@QFP100 [DX3021]
MCF52256AG80@QFP144 [DX3035]
MCF52256CAG66@QFP144 [DX3035]
MCF52258AG80@QFP144 [DX3035]
MCF52258CAG66@QFP144 [DX3035]
MCF52259CAG80@QFP144 [DX3035]
MCHC908JW32FC@TQFN48 [DX4021]
MCHC908JW32FCE@TQFN48 [DX4021]
MK10DN128VLH5@QFP64 [DX3011]
MK10DN512ZVLL10@QFP100 [DX3043]
MK10DX128VLF5@QFP48 [DX3007]
MK10DX128VLH5@QFP64 [DX3011]
MK10DX128VLH7@QFP64 [DX3011]
MK10DX256VLH7@QFP64 [DX3011]
MK10DX256VLL7@QFP100 [DX3043]
MK10DX64VLK7@QFP80 [DX3016]
MK10FN1M0VLQ12@QFP144 [DX3035]
MK11DN512VLK5@QFP80 [DX3016]
MK20DN512ZVLK10@QFP80 [DX3016]
MK20DN512ZVLL10@QFP100 [DX3043]
MK20DX128VLL7@QFP100 [DX3043]
MK20DX256VLH7@QFP64 [DX3011]
MK20DX256VMC7@FBGA121 [DX5232]
MK20DX256ZVLK10@QFP80 [DX3016]
MK20DX256ZVLL10@QFP100 [DX3043]
MK21DN512VLK5@QFP80 [DX3016]
MK22FN1M0VLL12@QFP100 [DX3043]
MK22FN256VLH12@QFP64 [DX3011]
MK22FN512VLL12@QFP100 [DX3043]
MK22FX512VMC12@BGA121 [DX5232]
MK40DN512VLK10@QFP80 [DX3016]
MK40DN512VLL10@QFP100 [DX3043]
MK40DN512VLQ10@QFP144 [DX3035]
MK40DX256VLH7@QFP64 [DX3011]
MK40DX256VMC7@FBGA121 [DX5232]
MK51DN512CLL10@QFP100 [DX3043]
MK51DN512CLQ10@QFP144 [DX3035]
MK51DX128CLH7@QFP64 [DX3011]
MK51DX256CLK7@QFP80 [DX3016]
MK51DX256CLL7@QFP100 [DX3043]
MK53DN512CLQ10@QFP144 [DX3035]
MK60DN512ZVLL10@QFP100 [DX3043]
MK60DN512ZVLQ10@QFP144 [DX3035]
MK60DX256ZVLL10@QFP100 [DX3043]
MK60DX256ZVLQ10@QFP144 [DX3035]
MK60FN1M0VLQ12@QFP144 [DX3035]
MK60FN1M0VLQ15@QFP144 [DX3035]
MK60FX512VLQ15@QFP144 [DX3035]
MM908E621ACDWB@SOIC54 [DX1060]
MM908E622ACDWB@SOIC54 [DX1060]
MM908E624ACDWB@SOIC54 [DX1060]
MM908E624ACEW@SOIC54 [DX1060]
MM908E624AYEW@SOIC54 [DX1060]
MM908E625AVDWB@SOIC54 [DX1060]
MM908E625AVEK@SOIC54 [DX1060]
MM908E626AVDWB@SOIC54 [DX1060]
MM908E626AVEK@SOIC54 [DX1060]
MM912F634BC1AE@QFP48 [DX3007-2]
MM912F634BC2AE@QFP48 [DX3007-2]
MM912F634BC3AE@QFP48 [DX3007-2]
MM912F634BV1AE@QFP48 [DX3007-2]
MM912F634BV2AE@QFP48 [DX3007-2]
MM912F634BV3AE@QFP48 [DX3007-2]
MM912F634CV1AE@QFP48 [DX3007-2]
MM912F634CV2AE@QFP48 [DX3007-2]
MM912F634CV2AP@QFP48 [DX3007-2]
MMPF0100NPAZES@QFN56 [DX4022-1]
MMPF0100NPZES@QFN56 [DX4022-1]
PC56F8011VFAE@QFP32 [DX3001]
PC56F8013VFAE@QFP32 [DX3001]
PC56F8014VFAE@QFP32 [DX3001]
PC9S08SG4CSC@SOIC8 [DX1030]
PC9S08SG4CSCE@SOIC8 [DX1030]
PC9S08SG4CTG@TSSOP16 [DX1000]
PC9S08SG4CTGE@TSSOP16 [DX1000]
PC9S08SG4CTJ@TSSOP20 [DX1000]
PC9S08SG4CTJE@TSSOP20 [DX1000]
PC9S08SG4MSC@SOIC8 [DX1030]
PC9S08SG4MSCE@SOIC8 [DX1030]
PC9S08SG4MTG@TSSOP16 [DX1000]
PC9S08SG4MTGE@TSSOP16 [DX1000]
PC9S08SG4MTJ@TSSOP20 [DX1000]
PC9S08SG4MTJE@TSSOP20 [DX1000]
PC9S08SG4VSC@SOIC8 [DX1030]
PC9S08SG4VSCE@SOIC8 [DX1030]
PC9S08SG4VTG@TSSOP16 [DX1000]

PC9S08SG4VTGE@TSSOP16 [DX1000]
PC9S08SG4VTJ@TSSOP20 [DX1000]
PC9S08SG4VTJE@TSSOP20 [DX1000]
PC9S08SG8CSC@SOIC8 [DX1030]
PC9S08SG8CSCE@SOIC8 [DX1030]
PC9S08SG8CTG@TSSOP16 [DX1000]
PC9S08SG8CTGE@TSSOP16 [DX1000]
PC9S08SG8CTJ@TSSOP20 [DX1000]
PC9S08SG8CTJE@TSSOP20 [DX1000]
PC9S08SG8MSC@SOIC8 [DX1030]
PC9S08SG8MSCE@SOIC8 [DX1030]
PC9S08SG8MTG@TSSOP16 [DX1000]
PC9S08SG8MTGE@TSSOP16 [DX1000]
PC9S08SG8MTJ@TSSOP20 [DX1000]
PC9S08SG8MTJE@TSSOP20 [DX1000]
PC9S08SG8VSC@SOIC8 [DX1030]
PC9S08SG8VSCE@SOIC8 [DX1030]
PC9S08SG8VTG@TSSOP16 [DX1000]
PC9S08SG8VTGE@TSSOP16 [DX1000]
PC9S08SG8VTJ@TSSOP20 [DX1000]
PC9S08SG8VTJE@TSSOP20 [DX1000]
PC9S08SH4CFK@QFN24 [DX4012]
PC9S08SH4CFK@QFN24(auto trim) [DX4012]
PC9S08SH4CFKE@QFN24 [DX4012]
PC9S08SH4CFKE@QFN24(auto trim) [DX4012]
PC9S08SH4CPJ
PC9S08SH4CPJ(auto trim)
PC9S08SH4CPJE
PC9S08SH4CPJE(auto trim)
PC9S08SH4CSC@SOIC8 [DX1030]
PC9S08SH4CSC@SOIC8(auto trim) [DX1030]
PC9S08SH4CSCE@SOIC8 [DX1030]
PC9S08SH4CSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4CTG@TSSOP16 [DX1000]
PC9S08SH4CTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4CTGE@TSSOP16 [DX1000]
PC9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4CTJ@TSSOP20 [DX1000]
PC9S08SH4CTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH4CTJE@TSSOP20 [DX1000]
PC9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4CWJ@SOIC20 [DX1033]
PC9S08SH4CWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4CWJE@SOIC20 [DX1033]
PC9S08SH4CWJE@SOIC20(auto trim) [DX1033]
PC9S08SH4MFK@QFN24 [DX4012]
PC9S08SH4MFK@QFN24(auto trim) [DX4012]
PC9S08SH4MFKE@QFN24 [DX4012]
PC9S08SH4MFKE@QFN24(auto trim) [DX4012]
PC9S08SH4MPJ
PC9S08SH4MPJ(auto trim)
PC9S08SH4MPJE
PC9S08SH4MPJE(auto trim)
PC9S08SH4MSC@SOIC8 [DX1030]
PC9S08SH4MSC@SOIC8(auto trim) [DX1030]
PC9S08SH4MSCE@SOIC8 [DX1030]
PC9S08SH4MSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4MTG@TSSOP16 [DX1000]
PC9S08SH4MTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4MTGE@TSSOP16 [DX1000]
PC9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4MTJ@TSSOP20 [DX1000]
PC9S08SH4MTJ@TSSOP20(auto trim) [DX1000]

PC9S08SH4MTJE@TSSOP20 [DX1000]
PC9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4MWJ@SOIC20 [DX1033]
PC9S08SH4MWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4MWJE@SOIC20 [DX1033]
PC9S08SH4MWJE@SOIC20(auto trim) [DX1033]
PC9S08SH4VFK@QFN24 [DX4012]
PC9S08SH4VFK@QFN24(auto trim) [DX4012]
PC9S08SH4VFKE@QFN24 [DX4012]
PC9S08SH4VFKE@QFN24(auto trim) [DX4012]
PC9S08SH4VPJ PC9S08SH4VPJ(auto trim)
PC9S08SH4VPJE PC9S08SH4VPJE(auto trim)
PC9S08SH4VSC@SOIC8 [DX1030]
PC9S08SH4VSC@SOIC8(auto trim) [DX1030]
PC9S08SH4VSCE@SOIC8 [DX1030]
PC9S08SH4VSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4VTG@TSSOP16 [DX1000]
PC9S08SH4VTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4VTGE@TSSOP16 [DX1000]
PC9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4VTJ@TSSOP20 [DX1000]
PC9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH4VTJE@TSSOP20 [DX1000]
PC9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4VWJ@SOIC20 [DX1033]
PC9S08SH4VWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4VWJE@SOIC20 [DX1033]
PC9S08SH4VWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8CFK@QFN24 [DX4012]
PC9S08SH8CFK@QFN24(auto trim) [DX4012]
PC9S08SH8CFKE@QFN24 [DX4012]
PC9S08SH8CFKE@QFN24(auto trim) [DX4012]
PC9S08SH8CPJ PC9S08SH8CPJ(auto trim)
PC9S08SH8CPJE PC9S08SH8CPJE(auto trim)
PC9S08SH8CSC@SOIC8 [DX1030]
PC9S08SH8CSC@SOIC8(auto trim) [DX1030]
PC9S08SH8CSCE@SOIC8 [DX1030]
PC9S08SH8CSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8CTG@TSSOP16 [DX1000]
PC9S08SH8CTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8CTGE@TSSOP16 [DX1000]
PC9S08SH8CTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8CTJ@TSSOP20 [DX1000]
PC9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8CTJE@TSSOP20 [DX1000]
PC9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8CWJ@SOIC20 [DX1033]
PC9S08SH8CWJ@SOIC20(auto trim) [DX1033]

PC9S08SH8CWJE@SOIC20 [DX1033]
PC9S08SH8CWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8MFK@QFN24 [DX4012]
PC9S08SH8MFK@QFN24(auto trim) [DX4012]
PC9S08SH8MFKE@QFN24 [DX4012]
PC9S08SH8MFKE@QFN24(auto trim) [DX4012]
PC9S08SH8MPJ PC9S08SH8MPJ(auto trim)
PC9S08SH8MPJE PC9S08SH8MPJE(auto trim)
PC9S08SH8MSC@SOIC8 [DX1030]
PC9S08SH8MSC@SOIC8(auto trim) [DX1030]
PC9S08SH8MSCE@SOIC8 [DX1030]
PC9S08SH8MSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8MTG@TSSOP16 [DX1000]
PC9S08SH8MTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8MTGE@TSSOP16 [DX1000]
PC9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8MTJ@TSSOP20 [DX1000]
PC9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8MTJE@TSSOP20 [DX1000]
PC9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8MWJ@SOIC20 [DX1033]
PC9S08SH8MWJ@SOIC20(auto trim) [DX1033]
PC9S08SH8MWJE@SOIC20 [DX1033]
PC9S08SH8MWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8VFK@QFN24 [DX4012]
PC9S08SH8VFK@QFN24(auto trim) [DX4012]
PC9S08SH8VFKE@QFN24 [DX4012]
PC9S08SH8VFKE@QFN24(auto trim) [DX4012]
PC9S08SH8VPJ PC9S08SH8VPJ(auto trim)
PC9S08SH8VPJE PC9S08SH8VPJE(auto trim)
PC9S08SH8VSC@SOIC8 [DX1030]
PC9S08SH8VSC@SOIC8(auto trim) [DX1030]
PC9S08SH8VSCE@SOIC8 [DX1030]
PC9S08SH8VSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8VTG@TSSOP16 [DX1000]
PC9S08SH8VTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8VTGE@TSSOP16 [DX1000]
PC9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8VTJ@TSSOP20 [DX1000]
PC9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8VTJE@TSSOP20 [DX1000]
PC9S08SH8VTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8VWJ@SOIC20 [DX1033]
PC9S08SH8VWJ@SOIC20(auto trim) [DX1033]
PC9S08SH8VWJE@SOIC20 [DX1033]
PC9S08SH8VWJE@SOIC20(auto trim) [DX1033]
PK40X256VLQ10@QFP144 [DX3035] PK60FN1M0VLQ12@QFP144 [DX3035]
S908QY2ACDT@TSSOP16 [DX1001]

S908QY2ACDT@TSSOP16(a-trim) [DX1001]
S908QY2ACDTE@TSSOP16 [DX1001]
S908QY2ACDTE@TSSOP16(a-trim) [DX1001]
S908QY2ACDW@SOIC16 [DX1072]
S908QY2ACDW@SOIC16(a-trim) [DX1072]
S908QY2ACDWE@SOIC16 [DX1072]
S908QY2ACDWE@SOIC16(a-trim) [DX1072]
S908QY2AMDT@TSSOP16 [DX1001]
S908QY2AMDT@TSSOP16(a-trim) [DX1001]
S908QY2AMDTE@TSSOP16 [DX1001]
S908QY2AMDTE@TSSOP16(a-trim) [DX1001]
S908QY2AMDW@SOIC16 [DX1072]
S908QY2AMDW@SOIC16(a-trim) [DX1072]
S908QY2AMDWE@SOIC16 [DX1072]
S908QY2AMDWE@SOIC16(a-trim) [DX1072]
S908QY2AVDT@TSSOP16 [DX1001]
S908QY2AVDT@TSSOP16(a-trim) [DX1001]
S908QY2AVDTE@TSSOP16 [DX1001]
S908QY2AVDTE@TSSOP16(a-trim) [DX1001]
S908QY2AVDW@SOIC16 [DX1072]
S908QY2AVDW@SOIC16(a-trim) [DX1072]
S908QY2AVDWE@SOIC16 [DX1072]
S908QY2AVDWE@SOIC16(a-trim) [DX1072]
S908QY4ACDT@TSSOP16 [DX1001]
S908QY4ACDT@TSSOP16(a-trim) [DX1001]
S908QY4ACDTE@TSSOP16 [DX1001]
S908QY4ACDTE@TSSOP16(a-trim) [DX1001]
S908QY4ACDW@SOIC16 [DX1072]
S908QY4ACDW@SOIC16(a-trim) [DX1072]
S908QY4ACDWE@SOIC16 [DX1072]
S908QY4ACDWE@SOIC16(a-trim) [DX1072]
S908QY4AMDT@TSSOP16 [DX1001]
S908QY4AMDT@TSSOP16(a-trim) [DX1001]
S908QY4AMDTE@TSSOP16 [DX1001]
S908QY4AMDTE@TSSOP16(a-trim) [DX1001]
S908QY4AMDW@SOIC16 [DX1072]
S908QY4AMDW@SOIC16(a-trim) [DX1072]
S908QY4AMDWE@SOIC16 [DX1072]
S908QY4AMDWE@SOIC16(a-trim) [DX1072]
S908QY4AVDT@TSSOP16 [DX1001]
S908QY4AVDT@TSSOP16(a-trim) [DX1001]
S908QY4AVDTE@TSSOP16 [DX1001]
S908QY4AVDTE@TSSOP16(a-trim) [DX1001]
S908QY4AVDW@SOIC16 [DX1072]
S908QY4AVDW@SOIC16(a-trim) [DX1072]
S908QY4AVDWE@SOIC16 [DX1072]
S908QY4AVDWE@SOIC16(a-trim) [DX1072]
S9S08AW16ACFT@QFN48 [DX4021]　　S9S08AW16ACLM@QFP32 [DX3001]

S9S08AW16ACLS@QFP44 [DX3003]
S9S08AW16ACLS@QFP44(*) [SA245A+B4404]
S9S08AW16AMFT@QFN48 [DX4021]　　S9S08AW16AMLM@QFP32 [DX3001]
S9S08AW16AMLS@QFP44 [DX3003]
S9S08AW16AMLS@QFP44(*) [SA245A+B4404]
S9S08AW16AVFT@QFN48 [DX4021]　　S9S08AW16AVLM@QFP32 [DX3001]
S9S08AW16AVLS@QFP44 [DX3003]
S9S08AW16AVLS@QFP44(*) [SA245A+B4404]
S9S08AW8ACFT@QFN48 [DX4021]　　S9S08AW8ACLM@QFP32 [DX3001]
S9S08AW8ACLS@QFP44 [DX3003]
S9S08AW8ACLS@QFP44(*) [SA245A+B4404]
S9S08AW8AMFT@QFN48 [DX4021]　　S9S08AW8AMLM@QFP32 [DX3001]
S9S08AW8AMLS@QFP44 [DX3003]
S9S08AW8AMLS@QFP44(*) [SA245A+B4404]
S9S08AW8AVFT@QFN48 [DX4021]　　S9S08AW8AVLM@QFP32 [DX3001]
S9S08AW8AVLS@QFP44 [DX3003]
S9S08AW8AVLS@QFP44(*) [SA245A+B4404]
S9S08SG4CSC@SOIC8 [DX1030]　　S9S08SG4CSCE@SOIC8 [DX1030]
S9S08SG4CTG@TSSOP16 [DX1000]　　S9S08SG4CTGE@TSSOP16 [DX1000]
S9S08SG4CTJ@TSSOP20 [DX1000]　　S9S08SG4CTJE@TSSOP20 [DX1000]
S9S08SG4MSC@SOIC8 [DX1030]　　S9S08SG4MSCE@SOIC8 [DX1030]
S9S08SG4MTG@TSSOP16 [DX1000]　　S9S08SG4MTGE@TSSOP16 [DX1000]
S9S08SG4MTJ@TSSOP20 [DX1000]　　S9S08SG4MTJE@TSSOP20 [DX1000]
S9S08SG4VSC@SOIC8 [DX1030]　　S9S08SG4VSCE@SOIC8 [DX1030]
S9S08SG4VTG@TSSOP16 [DX1000]　　S9S08SG4VTGE@TSSOP16 [DX1000]
S9S08SG4VTJ@TSSOP20 [DX1000]　　S9S08SG4VTJE@TSSOP20 [DX1000]
S9S08SG8CSC@SOIC8 [DX1030]　　S9S08SG8CSCE@SOIC8 [DX1030]
S9S08SG8CTG@TSSOP16 [DX1000]　　S9S08SG8CTGE@TSSOP16 [DX1000]
S9S08SG8CTJ@TSSOP20 [DX1000]　　S9S08SG8CTJE@TSSOP20 [DX1000]
S9S08SG8MSC@SOIC8 [DX1030]　　S9S08SG8MSCE@SOIC8 [DX1030]
S9S08SG8MTG@TSSOP16 [DX1000]　　S9S08SG8MTGE@TSSOP16 [DX1000]
S9S08SG8MTJ@TSSOP20 [DX1000]　　S9S08SG8MTJE@TSSOP20 [DX1000]
S9S08SG8VSC@SOIC8 [DX1030]　　S9S08SG8VSCE@SOIC8 [DX1030]
S9S08SG8VTG@TSSOP16 [DX1000]　　S9S08SG8VTGE@TSSOP16 [DX1000]
S9S08SG8VTJ@TSSOP20 [DX1000]　　S9S08SG8VTJE@TSSOP20 [DX1000]
S9S08SH4CFK@QFN24 [DX4012]
S9S08SH4CFK@QFN24(auto trim) [DX4012]
S9S08SH4CFKE@QFN24 [DX4012]
S9S08SH4CFKE@QFN24(auto trim) [DX4012]
S9S08SH4CPJ　　S9S08SH4CPJ(auto trim)
S9S08SH4CPJE　　S9S08SH4CPJE(auto trim)
S9S08SH4CSC@SOIC8 [DX1030]
S9S08SH4CSC@SOIC8(auto trim) [DX1030]
S9S08SH4CSCE@SOIC8 [DX1030]
S9S08SH4CSCE@SOIC8(auto trim) [DX1030]
S9S08SH4CTG@TSSOP16 [DX1000]
S9S08SH4CTG@TSSOP16(auto trim) [DX1000]
S9S08SH4CTGE@TSSOP16 [DX1000]

S9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4CTJ@TSSOP20 [DX1000]
S9S08SH4CTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4CTJE@TSSOP20 [DX1000]
S9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4CWJ@SOIC20 [DX1033]
S9S08SH4CWJ@SOIC20(auto trim) [DX1033]
S9S08SH4CWJE@SOIC20 [DX1033]
S9S08SH4CWJE@SOIC20(auto trim) [DX1033]
S9S08SH4MFK@QFN24 [DX4012]
S9S08SH4MFK@QFN24(auto trim) [DX4012]
S9S08SH4MFKE@QFN24 [DX4012]
S9S08SH4MFKE@QFN24(auto trim) [DX4012]
S9S08SH4MPJ S9S08SH4MPJ(auto trim)
S9S08SH4MPJE S9S08SH4MPJE(auto trim)
S9S08SH4MSC@SOIC8 [DX1030]
S9S08SH4MSC@SOIC8(auto trim) [DX1030]
S9S08SH4MSCE@SOIC8 [DX1030]
S9S08SH4MSCE@SOIC8(auto trim) [DX1030]
S9S08SH4MTG@TSSOP16 [DX1000]
S9S08SH4MTG@TSSOP16(auto trim) [DX1000]
S9S08SH4MTGE@TSSOP16 [DX1000]
S9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4MTJ@TSSOP20 [DX1000]
S9S08SH4MTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4MTJE@TSSOP20 [DX1000]
S9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4MWJ@SOIC20 [DX1033]
S9S08SH4MWJ@SOIC20(auto trim) [DX1033]
S9S08SH4MWJE@SOIC20 [DX1033]
S9S08SH4MWJE@SOIC20(auto trim) [DX1033]
S9S08SH4VFK@QFN24 [DX4012]
S9S08SH4VFK@QFN24(auto trim) [DX4012]
S9S08SH4VFKE@QFN24 [DX4012]
S9S08SH4VFKE@QFN24(auto trim) [DX4012]
S9S08SH4VPJ S9S08SH4VPJ(auto trim)
S9S08SH4VPJE S9S08SH4VPJE(auto trim)
S9S08SH4VSC@SOIC8 [DX1030]
S9S08SH4VSC@SOIC8(auto trim) [DX1030]
S9S08SH4VSCE@SOIC8 [DX1030]
S9S08SH4VSCE@SOIC8(auto trim) [DX1030]
S9S08SH4VTG@TSSOP16 [DX1000]
S9S08SH4VTG@TSSOP16(auto trim) [DX1000]
S9S08SH4VTGE@TSSOP16 [DX1000]
S9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4VTJ@TSSOP20 [DX1000]
S9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4VTJE@TSSOP20 [DX1000]

S9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4VWJ@SOIC20 [DX1033]
S9S08SH4VWJ@SOIC20(auto trim) [DX1033]
S9S08SH4VWJE@SOIC20 [DX1033]
S9S08SH4VWJE@SOIC20(auto trim) [DX1033]
S9S08SH8CFK@QFN24 [DX4012]
S9S08SH8CFK@QFN24(auto trim) [DX4012]
S9S08SH8CFKE@QFN24 [DX4012]
S9S08SH8CFKE@QFN24(auto trim) [DX4012]
S9S08SH8CPJ S9S08SH8CPJ(auto trim)
S9S08SH8CPJE S9S08SH8CPJE(auto trim)
S9S08SH8CSC@SOIC8 [DX1030]
S9S08SH8CSC@SOIC8(auto trim) [DX1030]
S9S08SH8CSCE@SOIC8 [DX1030]
S9S08SH8CSCE@SOIC8(auto trim) [DX1030]
S9S08SH8CTG@TSSOP16 [DX1000]
S9S08SH8CTG@TSSOP16(auto trim) [DX1000]
S9S08SH8CTGE@TSSOP16 [DX1000]
S9S08SH8CTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8CTJ@TSSOP20 [DX1000]
S9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8CTJE@TSSOP20 [DX1000]
S9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8CWJ@SOIC20 [DX1033]
S9S08SH8CWJ@SOIC20(auto trim) [DX1033]
S9S08SH8CWJE@SOIC20 [DX1033]
S9S08SH8CWJE@SOIC20(auto trim) [DX1033]
S9S08SH8MFK@QFN24 [DX4012]
S9S08SH8MFK@QFN24(auto trim) [DX4012]
S9S08SH8MFKE@QFN24 [DX4012]
S9S08SH8MFKE@QFN24(auto trim) [DX4012]
S9S08SH8MPJ S9S08SH8MPJ(auto trim)
S9S08SH8MPJE S9S08SH8MPJE(auto trim)
S9S08SH8MSC@SOIC8 [DX1030]
S9S08SH8MSC@SOIC8(auto trim) [DX1030]
S9S08SH8MSCE@SOIC8 [DX1030]
S9S08SH8MSCE@SOIC8(auto trim) [DX1030]
S9S08SH8MTG@TSSOP16 [DX1000]
S9S08SH8MTG@TSSOP16(auto trim) [DX1000]
S9S08SH8MTGE@TSSOP16 [DX1000]
S9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8MTJ@TSSOP20 [DX1000]
S9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8MTJE@TSSOP20 [DX1000]
S9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8MWJ@SOIC20 [DX1033]
S9S08SH8MWJ@SOIC20(auto trim) [DX1033]
S9S08SH8MWJE@SOIC20 [DX1033]

S9S08SH8MWJE@SOIC20(auto trim) [DX1033]
S9S08SH8VFK@QFN24 [DX4012]
S9S08SH8VFK@QFN24(auto trim) [DX4012]
S9S08SH8VFKE@QFN24 [DX4012]
S9S08SH8VFKE@QFN24(auto trim) [DX4012]
S9S08SH8VPJ S9S08SH8VPJ(auto trim)
S9S08SH8VPJE S9S08SH8VPJE(auto trim)
S9S08SH8VSC@SOIC8 [DX1030]
S9S08SH8VSC@SOIC8(auto trim) [DX1030]
S9S08SH8VSCE@SOIC8 [DX1030]
S9S08SH8VSCE@SOIC8(auto trim) [DX1030]
S9S08SH8VTG@TSSOP16 [DX1000]
S9S08SH8VTG@TSSOP16(auto trim) [DX1000]
S9S08SH8VTGE@TSSOP16 [DX1000]
S9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8VTJ@TSSOP20 [DX1000]
S9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8VTJE@TSSOP20 [DX1000]
S9S08SH8VTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8VWJ@SOIC20 [DX1033]
S9S08SH8VWJ@SOIC20(auto trim) [DX1033]
S9S08SH8VWJE@SOIC20 [DX1033]
S9S08SH8VWJE@SOIC20(auto trim) [DX1033]
S9S12P128CFT@QFN48 [DX4021] S9S12P128CLH@QFP64 [DX3011]
S9S12P128CQK@QFP80 [DX3018] S9S12P128MFT@QFN48 [DX4021]
S9S12P128MLH@QFP64 [DX3011] S9S12P128MQK@QFP80 [DX3018]
S9S12P128VFT@QFN48 [DX4021] S9S12P128VLH@QFP64 [DX3011]
S9S12P128VQK@QFP80 [DX3018] S9S12P32CFT@QFN48 [DX4021]
S9S12P32CLH@QFP64 [DX3011] S9S12P32CQK@QFP80 [DX3018]
S9S12P32MFT@QFN48 [DX4021] S9S12P32MLH@QFP64 [DX3011]
S9S12P32MQK@QFP80 [DX3018] S9S12P32VFT@QFN48 [DX4021]
S9S12P32VLH@QFP64 [DX3011] S9S12P32VQK@QFP80 [DX3018]
S9S12P64CFT@QFN48 [DX4021] S9S12P64CLH@QFP64 [DX3011]
S9S12P64CQK@QFP80 [DX3018] S9S12P64MFT@QFN48 [DX4021]
S9S12P64MLH@QFP64 [DX3011] S9S12P64MQK@QFP80 [DX3018]
S9S12P64VFT@QFN48 [DX4021] S9S12P64VLH@QFP64 [DX3011]
S9S12P64VQK@QFP80 [DX3018] S9S12P96CFT@QFN48 [DX4021]
S9S12P96CLH@QFP64 [DX3011] S9S12P96CQK@QFP80 [DX3018]
S9S12P96MFT@QFN48 [DX4021] S9S12P96MLH@QFP64 [DX3011]
S9S12P96MQK@QFP80 [DX3018] S9S12P96VFT@QFN48 [DX4021]
S9S12P96VLH@QFP64 [DX3011] S9S12P96VQK@QFP80 [DX3018]
SC101161DGCFU@TQFP80 [DX3018] SC101161DGCPV@TQFP112 [DX3026]
SC101161DGMFU@TQFP80 [DX3018] SC101161DGMPV@TQFP112 [DX3026]
SC101161DGVFU@TQFP80 [DX3018] SC101161DGVPV@TQFP112 [DX3026]
SC101161DJCFU@TQFP80 [DX3018] SC101161DJCPV@TQFP112 [DX3026]
SC101161DJMFU@TQFP80 [DX3018] SC101161DJMPV@TQFP112 [DX3026]
SC101161DJVFU@TQFP80 [DX3018] SC101161DJVPV@TQFP112 [DX3026]
SC101161DTCFU@TQFP80 [DX3018] SC101161DTCPV@TQFP112 [DX3026]

SC101161DTMFU@TQFP80 [DX3018]
SC101161DTVFU@TQFP80 [DX3018]
SC102202CFU@TQFP80 [DX3018]
SC102202MFU@TQFP80 [DX3018]
SC102202VFU@TQFP80 [DX3018]
SC102203CFU@TQFP80 [DX3018]
SC102203MFU@TQFP80 [DX3018]
SC102203VFU@TQFP80 [DX3018]
SC102204CFU@TQFP80 [DX3018]
SC102204MFU@TQFP80 [DX3018]
SC102204VFU@TQFP80 [DX3018]
SC102205CFU@TQFP80 [DX3018]
SC102205MFU@TQFP80 [DX3018]
SC102205VFU@TQFP80 [DX3018]
SC515846CFU@TQFP80 [DX3018]
SC515846MFU@TQFP80 [DX3018]
SC515846VFU@TQFP80 [DX3018]
SC515847CFU@TQFP80 [DX3018]
SC515847MFU@TQFP80 [DX3018]
SC515847VFU@TQFP80 [DX3018]
SC515848CFU@TQFP80 [DX3018]
SC515848MFU@TQFP80 [DX3018]
SC515848VFU@TQFP80 [DX3018]
SC515849CFU@TQFP80 [DX3018]
SC515849MFU@TQFP80 [DX3018]
SC515849VFU@TQFP80 [DX3018]
SC101161DTMPV@TQFP112 [DX3026]
SC101161DTVPV@TQFP112 [DX3026]
SC102202CPV@TQFP112 [DX3026]
SC102202MPV@TQFP112 [DX3026]
SC102202VPV@TQFP112 [DX3026]
SC102203CPV@TQFP112 [DX3026]
SC102203MPV@TQFP112 [DX3026]
SC102203VPV@TQFP112 [DX3026]
SC102204CPV@TQFP112 [DX3026]
SC102204MPV@TQFP112 [DX3026]
SC102204VPV@TQFP112 [DX3026]
SC102205CPV@TQFP112 [DX3026]
SC102205MPV@TQFP112 [DX3026]
SC102205VPV@TQFP112 [DX3026]
SC515846CPV@TQFP112 [DX3026]
SC515846MPV@TQFP112 [DX3026]
SC515846VPV@TQFP112 [DX3026]
SC515847CPV@TQFP112 [DX3026]
SC515847MPV@TQFP112 [DX3026]
SC515847VPV@TQFP112 [DX3026]
SC515848CPV@TQFP112 [DX3026]
SC515848MPV@TQFP112 [DX3026]
SC515848VPV@TQFP112 [DX3026]
SC515849CPV@TQFP112 [DX3026]
SC515849MPV@TQFP112 [DX3026]
SC515849VPV@TQFP112 [DX3026]
XC68HC705P6A(CDW)@SOIC28 [DX1033]
XC68HC711D3 [DX0001]
XC68HC711D3(3V) [DX0001]
XC68HC711D3(3V)@PLCC44 [DX2044]
XC68HC711D3(3V)@TQFP44 [DX3002]
XC68HC711D3@PLCC44 [DX2044]
XC68HC711D3@TQFP44 [DX3002]
XC68HSC705C9A [DX0001]
XC68HSC705C9A@PLCC44 [DX2044]
XC68HSC705C9A@TQFP44 [DX3002]

Fremont Micro Devices

E(E)PROM/FRAM/NVRAM

FT24C02 [DX0001]
FT24C02@SOP8 [DX1045]
FT24C02@TSSOP8 [DX1059]
FT24C02A [DX0001]
FT24C02A@SOP8 [DX1045]
FT24C02A@TSSOP8 [DX1059]
FT24C04 [DX0001]
FT24C04@SOP8 [DX1045]
FT24C04@TSSOP8 [DX1059]
FT24C04A [DX0001]
FT24C04A@SOP8 [DX1045]
FT24C04A@TSSOP8 [DX1059]
FT24C08 [DX0001]
FT24C08@SOP8 [DX1045]
FT24C08@TSSOP8 [DX1059]
FT24C08A [DX0001]
FT24C08A@SOP8 [DX1045]
FT24C08A@TSSOP8 [DX1059]
FT24C128 [DX0001]
FT24C128@SOP8 [DX1045]

FT24C128@TSSOP8 [DX1059]
FT24C128A [DX0001]
FT24C128A@SOP8 [DX1045]
FT24C128A@TSSOP8 [DX1059]
FT24C16 [DX0001]
FT24C16@SOP8 [DX1045]
FT24C16@TSSOP8 [DX1059]
FT24C16A [DX0001]
FT24C16A@SOP8 [DX1045]
FT24C16A@TSSOP8 [DX1059]
FT24C256 [DX0001]
FT24C256@SOP8 [DX1045]
FT24C256@TSSOP8 [DX1059]
FT24C256A [DX0001]
FT24C256A@SOP8 [DX1045]
FT24C256A@TSSOP8 [DX1059]
FT24C32 [DX0001]
FT24C32@SOP8 [DX1045]
FT24C32@TSSOP8 [DX1059]
FT24C32A [DX0001]
FT24C32A@SOP8 [DX1045]
FT24C32A@TSSOP8 [DX1059]
FT24C512A [DX0001]
FT24C512A@SOP8 [DX1045]
FT24C512A@TSSOP8 [DX1059]
FT24C64 [DX0001]
FT24C64@SOP8 [DX1045]
FT24C64@TSSOP8 [DX1059]
FT24C64A [DX0001]
FT24C64A@SOP8 [DX1045]
FT24C64A@TSSOP8 [DX1059]
FT25C016 [DX0001]
FT25C016@SOIC8 [DX1045]
FT25C016@TSSOP8 [DX1059]
FT25C016A [DX0001]
FT25C016A@SOIC8 [DX1045]
FT25C016A@TSSOP8 [DX1059]
FT25C064 [DX0001]
FT25C064@SOIC8 [DX1045]
FT25C064@TSSOP8 [DX1059]
FT25C064A [DX0001]
FT25C064A@SOIC8 [DX1045]
FT25C064A@TSSOP8 [DX1059]
FT25H16 [DX0001]
FT25H16@SOP8(150mil) [DX1045#1]
FT25H16@SOP8(200mil) [DX1044#1]
FT25H16@VSOP8 [DX1044#1]
FT34C02 [DX0001]
FT34C02@SOP8 [DX1045]
FT34C02@TSSOP8 [DX1059]
FT34C02A [DX0001]
FT34C02A@SOP8 [DX1045]
FT34C02A@TSSOP8 [DX1059]
FT93C46(08bit) [DX0001]
FT93C46(08bit)@SOP8 [DX1045]
FT93C46(08bit)@TSSOP8 [DX1059]
FT93C46(16bit) [DX0001]
FT93C46(16bit)@SOP8 [DX1045]
FT93C46(16bit)@TSSOP8 [DX1059]
FT93C46A(08bit) [DX0001]
FT93C46A(08bit)@SOP8 [DX1045]
FT93C46A(08bit)@TSSOP8 [DX1059]
FT93C46A(16bit) [DX0001]
FT93C46A(16bit)@SOP8 [DX1045]
FT93C46A(16bit)@TSSOP8 [DX1059]
FT93C56(08bit) [DX0001]
FT93C56(08bit)@SOP8 [DX1045]
FT93C56(08bit)@TSSOP8 [DX1059]
FT93C56(16bit) [DX0001]
FT93C56(16bit)@SOP8 [DX1045]
FT93C56(16bit)@TSSOP8 [DX1059]
FT93C56A(08bit) [DX0001]
FT93C56A(08bit)@SOP8 [DX1045]
FT93C56A(08bit)@TSSOP8 [DX1059]
FT93C56A(16bit) [DX0001]
FT93C56A(16bit)@SOP8 [DX1045]
FT93C56A(16bit)@TSSOP8 [DX1059]
FT93C66(08bit) [DX0001]
FT93C66(08bit)@SOIC8 [DX1045]
FT93C66(08bit)@TSSOP8 [DX1059]
FT93C66(16bit) [DX0001]
FT93C66(16bit)@SOP8 [DX1045]
FT93C66(16bit)@TSSOP8 [DX1059]
FT93C66A(08bit) [DX0001]
FT93C66A(08bit)@SOP8 [DX1045]
FT93C66A(08bit)@TSSOP8 [DX1059]
FT93C66A(16bit) [DX0001]
FT93C66A(16bit)@SOP8 [DX1045]
FT93C66A(16bit)@TSSOP8 [DX1059]
FT93C86(08bit) [DX0001]
FT93C86(08bit)@SOP8 [DX1045]
FT93C86(08bit)@TSSOP8 [DX1059]
FT93C86(16bit) [DX0001]
FT93C86(16bit)@SOP8 [DX1045]
FT93C86(16bit)@TSSOP8 [DX1059]
FT93C86A(08bit) [DX0001]

FT93C86A(08bit)@SOP8 [DX1045]
FT93C86A(08bit)@TSSOP8 [DX1059]
FT93C86A(16bit) [DX0001]
FT93C86A(16bit)@SOP8 [DX1045]
FT93C86A(16bit)@TSSOP8 [DX1059]

FTDICHIP

MICROCONTROLLER

VNC1L [DX3007-4]
VNC2-32L1B [DX3001]
VNC2-48L1B [DX3007-4]
VNC2L-32L1B [DX3001]
VNC2L-48L1B [DX3007-4]

FUDAN

E(E)PROM/FRAM/NVRAM

FM24C02A [DX0001]
FM24C02A@SOIC8 [DX1045]
FM24C02A@TSSOP8 [DX1059]
FM24C02B [DX0001]
FM24C02B@SOIC8 [DX1045]
FM24C02B@TSSOP8 [DX1059]
FM24C02C [DX0001]
FM24C02C@SOP8 [DX1045]
FM24C02C@TSSOP8 [DX1059]
FM24C02D [DX0001]
FM24C02D@SOP8 [DX1045]
FM24C02D@TSSOP8 [DX1059]
FM24C04A [DX0001]
FM24C04A@SOP8 [DX1045]
FM24C04A@TSSOP8 [DX1059]
FM24C04B [DX0001]
FM24C04B@SOIC8 [DX1045]
FM24C04B@TSSOP8 [DX1059]
FM24C04D [DX0001]
FM24C04D@SOP8 [DX1045]
FM24C04D@TSSOP8 [DX1059]
FM24C08A [DX0001]
FM24C08A@SOP8 [DX1045]
FM24C08A@TSSOP8 [DX1059]
FM24C08B [DX0001]
FM24C08B(ISP) [DX0001]
FM24C08B@SOIC8 [DX1045]
FM24C08B@TSSOP8 [DX1059]
FM24C08D [DX0001]
FM24C08D@SOP8 [DX1045]
FM24C08D@TSSOP8 [DX1059]
FM24C1024A [DX0001]
FM24C1024A@SOP8 [DX1045]
FM24C1024A@TSSOP [DX1059]
FM24C128A [DX0001]
FM24C128A@MSOP8 [DX1015]
FM24C128A@SOP8 [DX1045]
FM24C128A@TDFN8 [DX4047]
FM24C128A@TSSOP8 [DX1059]
FM24C16A [DX0001]
FM24C16A@SOIC8 [DX1045]
FM24C16A@TSSOP8 [DX1059]
FM24C16B [DX0001]
FM24C16B@SOIC8 [DX1045]
FM24C16B@TSSOP8 [DX1059]
FM24C16D [DX0001]
FM24C16D@SOP8 [DX1045]
FM24C16D@TSSOP8 [DX1059]
FM24C256A [DX0001]
FM24C256A@MSOP8 [DX1015]
FM24C256A@SOP8 [DX1045]
FM24C256A@TDFN8 [DX4047]
FM24C256A@TSSOP8 [DX1059]
FM24C32A [DX0001]
FM24C32A@SOIC8 [DX1045]
FM24C32A@TSSOP8 [DX1059]
FM24C512A [DX0001]
FM24C512A@SOP8 [DX1045]
FM24C512A@TSSOP8 [DX1059]
FM24C512D [DX0001]

FM24C512D@SOP8 [DX1045]
FM24C512D@TSSOP8 [DX1059]
FM24C64A [DX0001]
FM24C64A@SOIC8 [DX1045]
FM24C64A@TSSOP8 [DX1059]
FM25128 [DX0001]
FM25128@SOP8 [DX1045]
FM25128@TSSOP8 [DX1059]
FM25128@USON8 [DX4002]
FM25256 [DX0001]
FM25256@SOP8 [DX1045]
FM25256@TSSOP8 [DX1059]
FM25256@USON8 [DX4002]
FM25512@SOP8 [DX1045]
FM25512@TSSOP8 [DX1059]
FM25512@USON8 [DX4002]
FM25F005@SOP8 [DX1045#1]
FM25F005@TDFN8 [DX4002#1]
FM25F005@TSSOP8 [DX1059#1]
FM25F01@SOP8 [DX1045#1]
FM25F01@TDFN8 [DX4002#1]
FM25F01@TSSOP8 [DX1059#1]
FM25F02@SOP8(150mil) [DX1045#1]
FM25F02@SOP8(208mil) [DX1044#1]
FM25F02@TDFN8 [DX4005#1]
FM25F02A@SOP8(150mil) [DX1045#1]
FM25F02A@SOP8(208mil) [DX1044#1]
FM25F02A@TDFN8 [DX4005#1]
FM25F04@SOP8(150mil) [DX1045#1]
FM25F04@SOP8(208mil) [DX1044#1]
FM25F04@TDFN8 [DX4005#1]
FM25F04A@SOP8(150mil) [DX1045#1]
FM25F04A@SOP8(208mil) [DX1044#1]
FM25F04A@TDFN8 [DX4005#1]
FM25Q08@SOP8(150mil) [DX1045#1]
FM25Q08@SOP8(208mil) [DX1044#1]
FM25Q08@TDFN8 [DX4005#1]
FM25Q16@SOP8(150mil) [DX1045#1]
FM25Q16@SOP8(208mil) [DX1044#1]
FM25Q16@TDFN8 [DX4005#1]
FM25Q32@SOP8(150mil) [DX1045#1]
FM25Q32@SOP8(208mil) [DX1044#1]
FM25Q32@TDFN8 [DX4005#1]
FM93C46(08bit) [DX0001]
FM93C46(08bit)@SOP8 [DX1045]
FM93C46(08bit)@TDFN8 [DX4002]
FM93C46(08bit)@TSOT23-6L [DX1041]
FM93C46(08bit)@TSSOP8 [DX1059]
FM93C46(16bit) [DX0001]
FM93C46(16bit)@SOP8 [DX1045]
FM93C46(16bit)@TDFN8 [DX4002]
FM93C46(16bit)@TSOT23-6L [DX1041]
FM93C46(16bit)@TSSOP8 [DX1059]
FM93C56(08bit) [DX0001]
FM93C56(08bit)@SOP8 [DX1045]
FM93C56(08bit)@TDFN8 [DX4002]
FM93C56(08bit)@TSOT23-6L [DX1041]
FM93C56(08bit)@TSSOP8 [DX1059]
FM93C56(16bit) [DX0001]
FM93C56(16bit)@SOP8 [DX1045]
FM93C56(16bit)@TDFN8 [DX4002]
FM93C56(16bit)@TSOT23-6L [DX1041]
FM93C56(16bit)@TSSOP8 [DX1059]
FM93C66(08bit) [DX0001]
FM93C66(08bit)@SOP8 [DX1045]
FM93C66(08bit)@TDFN8 [DX4002]
FM93C66(08bit)@TSOT23-6L [DX1041]
FM93C66(08bit)@TSSOP8 [DX1059]
FM93C66(16bit) [DX0001]
FM93C66(16bit)@SOP8 [DX1045]
FM93C66(16bit)@TDFN8 [DX4002]
FM93C66(16bit)@TSOT23-6L [DX1041]
FM93C66(16bit)@TSSOP8 [DX1059]

FUJITSU

E(E)PROM/FRAM/NVRAM

MB84VD21081@FBGA61 [DX5048]
MB84VD21081EA@FBGA56 [DX5045]
MB84VD21081EM@FBGA56 [DX5045]
MB84VD21082@FBGA61 [DX5048]

MB84VD21082EA@FBGA56 [DX5045]
MB84VD21082EM@FBGA56 [DX5045]
MB84VD21083@FBGA61 [DX5048]
MB84VD21083EA@FBGA56 [DX5045]
MB84VD21083EM@FBGA56 [DX5045]
MB84VD21084@FBGA61 [DX5048]
MB84VD21084EA@FBGA56 [DX5045]
MB84VD21084EM@FBGA56 [DX5045]
MB84VD21091@FBGA61 [DX5048]
MB84VD21091EA@FBGA56 [DX5045]
MB84VD21091EM@FBGA56 [DX5045]
MB84VD21092@FBGA61 [DX5048]
MB84VD21092EA@FBGA56 [DX5045]
MB84VD21092EM@FBGA56 [DX5045]
MB84VD21093@FBGA61 [DX5048]
MB84VD21093EA@FBGA56 [DX5045]
MB84VD21093EM@FBGA56 [DX5045]
MB84VD21094@FBGA61 [DX5048]
MB84VD21094EA@FBGA56 [DX5045]
MB84VD21094EM@FBGA56 [DX5045]
MB84VD21181DA@FBGA69 [DX5001]
MB84VD21181EG@FBGA56 [DX5045]
MB84VD21181EM@FBGA56 [DX5045]
MB84VD21182DA@FBGA69 [DX5001]
MB84VD21182EG@FBGA56 [DX5045]
MB84VD21182EM@FBGA56 [DX5045]
MB84VD21183DA@FBGA69 [DX5001]
MB84VD21183EG@FBGA56 [DX5045]
MB84VD21183EM@FBGA56 [DX5045]
MB84VD21184DA@FBGA69 [DX5001]
MB84VD21184EG@FBGA56 [DX5045]
MB84VD21184EM@FBGA56 [DX5045]
MB84VD21191DA@FBGA69 [DX5001]
MB84VD21191EG@FBGA56 [DX5045]
MB84VD21191EM@FBGA56 [DX5045]
MB84VD21192DA@FBGA69 [DX5001]
MB84VD21192EG@FBGA56 [DX5045]
MB84VD21192EM@FBGA56 [DX5045]
MB84VD21193DA@FBGA69 [DX5001]
MB84VD21193EG@FBGA56 [DX5045]
MB84VD21193EM@FBGA56 [DX5045]
MB84VD21194DA@FBGA69 [DX5001]
MB84VD21194EG@FBGA56 [DX5045]
MB84VD21194EM@FBGA56 [DX5045]
MB84VD22180FA@FBGA59 [DX5045]
MB84VD22180FM@FBGA59 [DX5045]
MB84VD22181EB@FBGA73 [DX5001]
MB84VD22181EC@FBGA73 [DX5001]
MB84VD22181EE@FBGA73 [DX5001]
MB84VD22181FM@FBGA56 [DX5045]
MB84VD22182EB@FBGA73 [DX5001]
MB84VD22182EC@FBGA73 [DX5001]
MB84VD22182EE@FBGA73 [DX5001]
MB84VD22183EB@FBGA73 [DX5001]
MB84VD22183EC@FBGA73 [DX5001]
MB84VD22183EE@FBGA73 [DX5001]
MB84VD22184EB@FBGA73 [DX5001]
MB84VD22184EC@FBGA73 [DX5001]
MB84VD22184EE@FBGA73 [DX5001]
MB84VD22184FM@FBGA56 [DX5045]
MB84VD22190FA@FBGA59 [DX5045]
MB84VD22190FM@FBGA59 [DX5045]
MB84VD22191EB@FBGA73 [DX5001]
MB84VD22191EC@FBGA73 [DX5001]
MB84VD22191EE@FBGA73 [DX5001]
MB84VD22191FM@FBGA56 [DX5045]
MB84VD22192EB@FBGA73 [DX5001]
MB84VD22192EC@FBGA73 [DX5001]
MB84VD22192EE@FBGA73 [DX5001]
MB84VD22193EB@FBGA73 [DX5001]
MB84VD22193EC@FBGA73 [DX5001]
MB84VD22193EE@FBGA73 [DX5001]
MB84VD22194EB@FBGA73 [DX5001]
MB84VD22194EC@FBGA73 [DX5001]
MB84VD22194EE@FBGA73 [DX5001]
MB84VD22194FM@FBGA56 [DX5045]
MB84VD22280FA@FBGA59 [DX5045]
MB84VD22280FE@FBGA59 [DX5045]
MB84VD22282EA@FBGA71 [DX5001]
MB84VD22282EE@FBGA71 [DX5001]
MB84VD22283EA@FBGA71 [DX5001]
MB84VD22283EE@FBGA71 [DX5001]
MB84VD22284EA@FBGA71 [DX5001]
MB84VD22284EE@FBGA71 [DX5001]
MB84VD22290FA@FBGA59 [DX5045]
MB84VD22290FE@FBGA59 [DX5045]
MB84VD22292EA@FBGA71 [DX5001]
MB84VD22292EE@FBGA71 [DX5001]
MB84VD22293EA@FBGA71 [DX5001]
MB84VD22293EE@FBGA71 [DX5001]
MB84VD22294EA@FBGA71 [DX5001]
MB84VD22294EE@FBGA71 [DX5001]
MB84VD22386EJ@FBGA71 [DX5001]
MB84VD22387EJ@FBGA71 [DX5001]
MB84VD22388EJ@FBGA71 [DX5001]
MB84VD22396EJ@FBGA71 [DX5001]

MB84VD22397EJ@FBGA71 [DX5001]
MB84VD22398EJ@FBGA71 [DX5001]
MB84VD23180FM@FBGA73 [DX5001]
MB84VD23280EA@FBGA101 [DX5076]
MB84VD23280EE@FBGA101 [DX5076]
MB84VD23280FA@FBGA65 [DX5048]
MB84VD23381EJ@FBGA101 [DX5076]
MB84VD23381FJ@FBGA65 [DX5048]
MB84VD23381HJ@FBGA56 [DX5045]
MB84VD23481FJ@FBGA65 [DX5048]
MB84VD23581FJ@FBGA65 [DX5048]
MB84VP23481FK@FBGA65 [DX5048]
MB84VP24481HK@FBGA73 [DX5001]
MB84VP24491HK@FBGA73 [DX5001]
MB85R256@SOP28 [DX1035]
MB85R256@TSOP28 [DX1001]
MB85R256A@SOP28 [DX1035]
MB85R256A@TSOP28 [DX1001]
MB85RC128 [DX0001]
MB85RC128@SOIC8 [DX1045]
MB85RC16 [DX0001]
MB85RC16@SOIC8 [DX1045]
MB85RC64 [DX0001]
MB85RC64@SOIC8 [DX1045]
MBM2212 [DX0001]
MBM271001 [DX0001]
MBM271001@PLCC32 [DX2032]
MBM271001@TSOP32 [DX1002]
MBM27128 [DX0001]
MBM27128@PLCC32 [DX2032]
MBM2716 [DX0001]
MBM2716H [DX0001]
MBM27256 [DX0001]
MBM27256@PLCC32 [DX2032]
MBM2732 [DX0001]
MBM2732A [DX0001]
MBM2764 [DX0001]
MBM2764@PLCC32 [DX2032]
MBM27C1000 [DX0001]
MBM27C1000@PLCC32 [DX2032]
MBM27C1000@TSOP32 [DX1002]
MBM27C1001 [DX0001]
MBM27C1001@PLCC32 [DX2032]
MBM27C1001@TSOP32 [DX1002]
MBM27C1024 [DX0001]
MBM27C1024@PLCC44 [DX2044]
MBM27C128 [DX0001]
MBM27C128@PLCC32 [DX2032]
MBM27C128P [DX0001]
MBM27C128P@PLCC32 [DX2032]
MBM27C2000 [DX0001]
MBM27C2000@PLCC32 [DX2032]
MBM27C2000@TSOP32 [DX1002]
MBM27C2001 [DX0001]
MBM27C2001@PLCC32 [DX2032]
MBM27C2001@TSOP32 [DX1002]
MBM27C2048 [DX0001]
MBM27C256 [DX0001]
MBM27C256@PLCC32 [DX2032]
MBM27C256A [DX0001]
MBM27C256A@PLCC32 [DX2032]
MBM27C256AP [DX0001]
MBM27C256AP@PLCC32 [DX2032]
MBM27C256H [DX0001]
MBM27C256H@PLCC32 [DX2032]
MBM27C32A [DX0001]
MBM27C4001 [DX0001]
MBM27C4001@PLCC32 [DX2032]
MBM27C4001@TSOP32 [DX1002]
MBM27C4096 [DX0001]
MBM27C512 [DX0001]
MBM27C512@PLCC32 [DX2032]
MBM27C512P [DX0001]
MBM27C512P@PLCC32 [DX2032]
MBM27C64 [DX0001]
MBM27C64@PLCC32 [DX2032]
MBM28C64 [DX0001]
MBM28C65 [DX0001]
MBM28F010 [DX0001]
MBM28F010(REVERSE)@TSOP32 [DX1002]
MBM28F010@PLCC32 [DX2032]
MBM28F010@SOP32 [DX1019]
MBM28F010@TSOP32 [DX1002]
MBM29DL161BD(REVERSE)@TSOP48 [DX1004]
MBM29DL161BD@FBGA48 [DX5002]
MBM29DL161BD@TSOP48 [DX1004]
MBM29DL161BE(REVERSE)@TSOP48 [DX1004]
MBM29DL161BE@FBGA48 [DX5002]
MBM29DL161BE@TSOP48 [DX1004]
MBM29DL161TD(REVERSE)@TSOP48 [DX1004]

MBM29DL161TD@FBGA48 [DX5002]　　MBM29DL161TD@TSOP48 [DX1004]
MBM29DL161TE(REVERSE)@TSOP48 [DX1004]
MBM29DL161TE@FBGA48 [DX5002]　　MBM29DL161TE@TSOP48 [DX1004]
MBM29DL162BD(REVERSE)@TSOP48 [DX1004]
MBM29DL162BD@FBGA48 [DX5002]　　MBM29DL162BD@TSOP48 [DX1004]
MBM29DL162BE(REVERSE)@TSOP48 [DX1004]
MBM29DL162BE@FBGA48 [DX5002]　　MBM29DL162BE@TSOP48 [DX1004]
MBM29DL162TD(REVERSE)@TSOP48 [DX1004]
MBM29DL162TD@FBGA48 [DX5002]　　MBM29DL162TD@TSOP48 [DX1004]
MBM29DL162TE(REVERSE)@TSOP48 [DX1004]
MBM29DL162TE@FBGA48 [DX5002]　　MBM29DL162TE@TSOP48 [DX1004]
MBM29DL163BD(REVERSE)@TSOP48 [DX1004]
MBM29DL163BD@FBGA48 [DX5002]　　MBM29DL163BD@TSOP48 [DX1004]
MBM29DL163BE(REVERSE)@TSOP48 [DX1004]
MBM29DL163BE@FBGA48 [DX5002]　　MBM29DL163BE@TSOP48 [DX1004]
MBM29DL163TD(REVERSE)@TSOP48 [DX1004]
MBM29DL163TD@FBGA48 [DX5002]　　MBM29DL163TD@TSOP48 [DX1004]
MBM29DL163TE(REVERSE)@TSOP48 [DX1004]
MBM29DL163TE@FBGA48 [DX5002]　　MBM29DL163TE@TSOP48 [DX1004]
MBM29DL164BD(REVERSE)@TSOP48 [DX1004]
MBM29DL164BD@FBGA48 [DX5002]　　MBM29DL164BD@TSOP48 [DX1004]
MBM29DL164BE(REVERSE)@TSOP48 [DX1004]
MBM29DL164BE@FBGA48 [DX5002]　　MBM29DL164BE@TSOP48 [DX1004]
MBM29DL164TD(REVERSE)@TSOP48 [DX1004]
MBM29DL164TD@FBGA48 [DX5002]　　MBM29DL164TD@TSOP48 [DX1004]
MBM29DL164TE(REVERSE)@TSOP48 [DX1004]
MBM29DL164TE@FBGA48 [DX5002]　　MBM29DL164TE@TSOP48 [DX1004]
MBM29DL320BF@FBGA48 [DX5039]　　MBM29DL320BF@TSOP48 [DX1004]
MBM29DL320TF@FBGA48 [DX5039]　　MBM29DL320TF@TSOP48 [DX1004]
MBM29DL321BD(REVERSE)@TSOP48 [DX1004]
MBM29DL321BD@FBGA63 [DX5047]　　MBM29DL321BD@TSOP48 [DX1004]
MBM29DL321BE(REVERSE)@TSOP48 [DX1004]
MBM29DL321BE@FBGA63 [DX5047]　　MBM29DL321BE@TSOP48 [DX1004]
MBM29DL321TD(REVERSE)@TSOP48 [DX1004]
MBM29DL321TD@FBGA63 [DX5047]　　MBM29DL321TD@TSOP48 [DX1004]
MBM29DL321TE(REVERSE)@TSOP48 [DX1004]
MBM29DL321TE@FBGA63 [DX5047]　　MBM29DL321TE@TSOP48 [DX1004]
MBM29DL322BD(REVERSE)@TSOP48 [DX1004]
MBM29DL322BD@FBGA63 [DX5047]　　MBM29DL322BD@TSOP48 [DX1004]
MBM29DL322BE(REVERSE)@TSOP48 [DX1004]
MBM29DL322BE@FBGA63 [DX5047]　　MBM29DL322BE@TSOP48 [DX1004]
MBM29DL322TD(REVERSE)@TSOP48 [DX1004]
MBM29DL322TD@FBGA63 [DX5047]　　MBM29DL322TD@TSOP48 [DX1004]
MBM29DL322TE(REVERSE)@TSOP48 [DX1004]
MBM29DL322TE@FBGA63 [DX5047]　　MBM29DL322TE@TSOP48 [DX1004]
MBM29DL323BD(REVERSE)@TSOP48 [DX1004]
MBM29DL323BD@FBGA63 [DX5047]　　MBM29DL323BD@TSOP48 [DX1004]
MBM29DL323BE(REVERSE)@TSOP48 [DX1004]

MBM29DL323BE@FBGA63 [DX5047]
MBM29DL323BE@TSOP48 [DX1004]
MBM29DL323BF@FBGA48 [DX5039]
MBM29DL323BF@TSOP48 [DX1004]
MBM29DL323TD(REVERSE)@TSOP48 [DX1004]
MBM29DL323TD@FBGA63 [DX5047]
MBM29DL323TD@TSOP48 [DX1004]
MBM29DL323TE(REVERSE)@TSOP48 [DX1004]
MBM29DL323TE@FBGA63 [DX5047]
MBM29DL323TE@TSOP48 [DX1004]
MBM29DL323TF@FBGA48 [DX5039]
MBM29DL323TF@TSOP48 [DX1004]
MBM29DL324BD(REVERSE)@TSOP48 [DX1004]
MBM29DL324BD@FBGA63 [DX5047]
MBM29DL324BD@TSOP48 [DX1004]
MBM29DL324BE(REVERSE)@TSOP48 [DX1004]
MBM29DL324BE@FBGA63 [DX5047]
MBM29DL324BE@TSOP48 [DX1004]
MBM29DL324TD(REVERSE)@TSOP48 [DX1004]
MBM29DL324TD@FBGA63 [DX5047]
MBM29DL324TD@TSOP48 [DX1004]
MBM29DL324TE(REVERSE)@TSOP48 [DX1004]
MBM29DL324TE@FBGA63 [DX5047]
MBM29DL324TE@TSOP48 [DX1004]
MBM29DL32BF@FBGA48 [DX5039]
MBM29DL32BF@TSOP48 [DX1004]
MBM29DL32TF@FBGA48 [DX5039]
MBM29DL32TF@TSOP48 [DX1004]
MBM29DL34BF@FBGA48 [DX5039]
MBM29DL34BF@TSOP48 [DX1004]
MBM29DL34TF@FBGA48 [DX5039]
MBM29DL34TF@TSOP48 [DX1004]
MBM29DL400BB@PSOP44 [DX1014]
MBM29DL400BB@TSOP48 [DX1004]
MBM29DL400BC(REVERSE)@TSOP48 [DX1004]
MBM29DL400BC@PSOP44 [DX1014]
MBM29DL400BC@TSOP48 [DX1004]
MBM29DL400BT@PSOP44 [DX1014]
MBM29DL400BT@TSOP48 [DX1004]
MBM29DL400TC(REVERSE)@TSOP48 [DX1004]
MBM29DL400TC@PSOP44 [DX1014]
MBM29DL400TC@TSOP48 [DX1004]
MBM29DL640E(REVERSE)@TSOP48 [DX1004]
MBM29DL640E@FBGA63 [DX5041]
MBM29DL640E@TSOP48 [DX1004]
MBM29DL64DF@FBGA48 [DX5022]
MBM29DL64DF@TSOP48 [DX1004]
MBM29DL800B@PSOP44 [DX1014]
MBM29DL800B@TSOP48 [DX1004]
MBM29DL800BA(REVERSE)@TSOP48 [DX1004]
MBM29DL800BA@FBGA48 [DX5039]
MBM29DL800BA@PSOP44 [DX1014]
MBM29DL800BA@TSOP48 [DX1004]
MBM29DL800BB@PSOP44 [DX1014]
MBM29DL800BB@TSOP48 [DX1004]
MBM29DL800BT@PSOP44 [DX1014]
MBM29DL800BT@TSOP48 [DX1004]
MBM29DL800T@PSOP44 [DX1014]
MBM29DL800T@TSOP48 [DX1004]
MBM29DL800TA(REVERSE)@TSOP48 [DX1004]
MBM29DL800TA@FBGA48 [DX5039]
MBM29DL800TA@PSOP44 [DX1014]
MBM29DL800TA@TSOP48 [DX1004]
MBM29DS163BE@FBGA48 [DX5043]
MBM29DS163BE@TSOP48 [DX1004]
MBM29DS163TE@FBGA48 [DX5043]
MBM29DS163TE@TSOP48 [DX1004]
MBM29F001B [DX0001]
MBM29F001B@PLCC32 [DX2032]
MBM29F001B@TSOP32 [DX1002]
MBM29F001T [DX0001]
MBM29F001T@PLCC32 [DX2032]
MBM29F001T@TSOP32 [DX1002]
MBM29F002B [DX0001]
MBM29F002B@PLCC32 [DX2032]
MBM29F002B@TSOP32 [DX1002]
MBM29F002NB [DX0001]
MBM29F002NB@PLCC32 [DX2032]
MBM29F002NB@TSOP32 [DX1002]
MBM29F002NT [DX0001]
MBM29F002NT@PLCC32 [DX2032]
MBM29F002NT@TSOP32 [DX1002]
MBM29F002T [DX0001]
MBM29F002T@PLCC32 [DX2032]

MBM29F002T@TSOP32 [DX1002]
MBM29F010 [DX0001]
MBM29F010@PLCC32 [DX2032]
MBM29F010@TSOP32 [DX1002]
MBM29F010A [DX0001]
MBM29F010A@PLCC32 [DX2032]
MBM29F010A@TSOP32 [DX1002]
MBM29F016@PSOP44 [DX1014]
MBM29F016@TSOP40 [DX1006]
MBM29F016@TSOP48 [DX1004]
MBM29F016A@PSOP44 [DX1014]
MBM29F016A@TSOP40 [DX1006]
MBM29F016A@TSOP48 [DX1004]
MBM29F016B@PSOP44 [DX1014]
MBM29F016B@TSOP40 [DX1006]
MBM29F016B@TSOP48 [DX1004]
MBM29F017A(REVERSE)@TSOP48 [DX1004]
MBM29F017A@TSOP48 [DX1004]
MBM29F017B@TSOP48 [DX1004]
MBM29F017D@TSOP40 [DX1006]
MBM29F017D@TSOP48 [DX1004]
MBM29F032B@PSOP44 [DX1014]
MBM29F032B@TSOP40 [DX1006]
MBM29F033C@TSOP40 [DX1006]
MBM29F040 [DX0001]
MBM29F040@PLCC32 [DX2032]
MBM29F040@TSOP32 [DX1002]
MBM29F040B [DX0001]
MBM29F040B@PLCC32 [DX2032]
MBM29F040B@TSOP32 [DX1002]
MBM29F040C@PLCC32 [DX2032]
MBM29F040C@TSOP32 [DX1002]
MBM29F080@PSOP44 [DX1014]
MBM29F080@TSOP40 [DX1006]
MBM29F080A(REVERSE)@TSOP40 [DX1006]
MBM29F080A(REVERSE)@TSOP48 [DX1004]
MBM29F080A@PSOP44 [DX1014]
MBM29F080A@TSOP40 [DX1006]
MBM29F080A@TSOP48 [DX1004]
MBM29F080B@PSOP44 [DX1014]
MBM29F080B@TSOP40 [DX1006]
MBM29F100B@PSOP44 [DX1014]
MBM29F100B@TSOP48 [DX1004]
MBM29F100T@PSOP44 [DX1014]
MBM29F100T@TSOP48 [DX1004]
MBM29F160BE(REVERSE)@TSOP48 [DX1004]
MBM29F160BE@TSOP48 [DX1004]
MBM29F160TE(REVERSE)@TSOP48 [DX1004]
MBM29F160TE@TSOP48 [DX1004]
MBM29F200AB@PSOP44 [DX1014]
MBM29F200AB@TSOP48 [DX1004]
MBM29F200AT@PSOP44 [DX1014]
MBM29F200AT@TSOP48 [DX1004]
MBM29F200B@PSOP44 [DX1014]
MBM29F200B@TSOP48 [DX1004]
MBM29F200BC(REVERSE)@TSOP48 [DX1004]
MBM29F200BC@PSOP44 [DX1014]
MBM29F200BC@TSOP48 [DX1004]
MBM29F200T@PSOP44 [DX1014]
MBM29F200T@TSOP48 [DX1004]
MBM29F200TC(REVERSE)@TSOP48 [DX1004]
MBM29F200TC@PSOP44 [DX1014]
MBM29F200TC@TSOP48 [DX1004]
MBM29F400AB@PSOP44 [DX1014]
MBM29F400AB@TSOP48 [DX1004]
MBM29F400AT@PSOP44 [DX1014]
MBM29F400AT@TSOP48 [DX1004]
MBM29F400B@PSOP44 [DX1014]
MBM29F400B@TSOP48 [DX1004]
MBM29F400BB@PSOP44 [DX1014]
MBM29F400BB@TSOP48 [DX1004]
MBM29F400BC(REVERSE)@TSOP48 [DX1004]
MBM29F400BC@PSOP44 [DX1014]
MBM29F400BC@TSOP48 [DX1004]
MBM29F400BT@PSOP44 [DX1014]
MBM29F400BT@TSOP48 [DX1004]
MBM29F400T@PSOP44 [DX1014]
MBM29F400T@TSOP48 [DX1004]
MBM29F400TC(REVERSE)@TSOP48 [DX1004]
MBM29F400TC@PSOP44 [DX1014]
MBM29F400TC@TSOP48 [DX1004]
MBM29F800B@PSOP44 [DX1014]
MBM29F800B@TSOP48 [DX1004]

MBM29F800BA(REVERSE)@TSOP48 [DX1004]
MBM29F800BA@PSOP44 [DX1014]　　MBM29F800BA@TSOP48 [DX1004]
MBM29F800BB@PSOP44 [DX1014]　　MBM29F800BB@TSOP48 [DX1004]
MBM29F800BT@PSOP44 [DX1014]　　MBM29F800BT@TSOP48 [DX1004]
MBM29F800T@PSOP44 [DX1014]　　MBM29F800T@TSOP48 [DX1004]
MBM29F800TA(REVERSE)@TSOP48 [DX1004]
MBM29F800TA@PSOP44 [DX1014]　　MBM29F800TA@TSOP48 [DX1004]
MBM29LL800B@TSOP48 [DX1004]　　MBM29LL800BB@TSOP48 [DX1004]
MBM29LL800BT@TSOP48 [DX1004]　　MBM29LL800T@TSOP48 [DX1004]
MBM29LV001B@PLCC32 [DX2032]
MBM29LV001BB(REVERSE)@TSOP32 [DX1002]
MBM29LV001BB@PLCC32 [DX2032]　　MBM29LV001BB@TSOP32 [DX1002]
MBM29LV001BC(REVERSE)@TSOP32 [DX1002]
MBM29LV001BC@PLCC32 [DX2032]　　MBM29LV001BC@TSOP32 [DX1002]
MBM29LV001BT(REVERSE)@TSOP32 [DX1002]
MBM29LV001BT@PLCC32 [DX2032]　　MBM29LV001BT@TSOP32 [DX1002]
MBM29LV001T@TSOP32 [DX1002]
MBM29LV001TC(REVERSE)@TSOP32 [DX1002]
MBM29LV001TC@PLCC32 [DX2032]　　MBM29LV001TC@TSOP32 [DX1002]
MBM29LV002B@TSOP40 [DX1006]　　MBM29LV002T@TSOP40 [DX1006]
MBM29LV004B@TSOP40 [DX1006]　　MBM29LV004BB@TSOP40 [DX1006]
MBM29LV004BT@TSOP40 [DX1006]　　MBM29LV004T@TSOP40 [DX1006]
MBM29LV008B@TSOP40 [DX1006]　　MBM29LV008BB@TSOP40 [DX1006]
MBM29LV008BT@TSOP40 [DX1006]　　MBM29LV008T@TSOP40 [DX1006]
MBM29LV016/B@TSOP40 [DX1006]　　MBM29LV016/T@TSOP40 [DX1006]
MBM29LV016B@TSOP40 [DX1006]　　MBM29LV017@FBGA48 [DX5022]
MBM29LV017@TSOP40 [DX1006]　　MBM29LV017B@TSOP40 [DX1006]
MBM29LV017E@TSOP40 [DX1006]　　MBM29LV033C@TSOP40 [DX1006]
MBM29LV080@TSOP40 [DX1006]　　MBM29LV080A@TSOP40 [DX1006]
MBM29LV081@TSOP40 [DX1006]　　MBM29LV081B@TSOP40 [DX1006]
MBM29LV116B@TSOP40 [DX1006]
MBM29LV160B(REVERSE)@TSOP48 [DX1004]
MBM29LV160B@FBGA48 [DX5022]　　MBM29LV160B@TSOP48 [DX1004]
MBM29LV160BE(REVERSE)@TSOP48 [DX1004]
MBM29LV160BE@FBGA48 [DX5002]　　MBM29LV160BE@PSOP44 [DX1014]
MBM29LV160BE@TSOP48 [DX1004]　　MBM29LV160BM@FBGA48 [DX5002]
MBM29LV160BM@TSOP48 [DX1004]
MBM29LV160T(REVERSE)@TSOP48 [DX1004]
MBM29LV160T@FBGA48 [DX5022]　　MBM29LV160T@TSOP48 [DX1004]
MBM29LV160TE(REVERSE)@TSOP48 [DX1004]
MBM29LV160TE@FBGA48 [DX5002]　　MBM29LV160TE@PSOP44 [DX1014]
MBM29LV160TE@TSOP48 [DX1004]　　MBM29LV160TM@FBGA48 [DX5002]
MBM29LV160TM@TSOP48 [DX1004]　　MBM29LV200B@PSOP44 [DX1014]
MBM29LV200B@TSOP48 [DX1004]　　MBM29LV200BB@PSOP44 [DX1014]
MBM29LV200BB@TSOP48 [DX1004]
MBM29LV200BC(REVERSE)@TSOP48 [DX1004]
MBM29LV200BC@PSOP44 [DX1014]　　MBM29LV200BC@TSOP48 [DX1004]
MBM29LV200BT@PSOP44 [DX1014]　　MBM29LV200BT@TSOP48 [DX1004]

MBM29LV200T@PSOP44 [DX1014]　　MBM29LV200T@TSOP48 [DX1004]
MBM29LV200TC(REVERSE)@TSOP48 [DX1004]
MBM29LV200TC@PSOP44 [DX1014]　　MBM29LV200TC@TSOP48 [DX1004]
MBM29LV320BE(REVERSE)@TSOP48 [DX1004]
MBM29LV320BE@FBGA63 [DX5063]　　MBM29LV320BE@TSOP48 [DX1004]
MBM29LV320TE(REVERSE)@TSOP48 [DX1004]
MBM29LV320TE@FBGA63 [DX5063]　　MBM29LV320TE@TSOP48 [DX1004]
MBM29LV400B@PSOP44 [DX1014]　　MBM29LV400B@TSOP48 [DX1004]
MBM29LV400BB@PSOP44 [DX1014]　　MBM29LV400BB@TSOP48 [DX1004]
MBM29LV400BC@FBGA48 [DX5002]　　MBM29LV400BC@PSOP44 [DX1014]
MBM29LV400BC@TSOP48 [DX1004]　　MBM29LV400BT@PSOP44 [DX1014]
MBM29LV400BT@TSOP48 [DX1004]　　MBM29LV400T@PSOP44 [DX1014]
MBM29LV400T@TSOP48 [DX1004]　　MBM29LV400TC@FBGA48 [DX5002]
MBM29LV400TC@PSOP44 [DX1014]　　MBM29LV400TC@TSOP48 [DX1004]
MBM29LV650UE(REVERSE)@TSOP48 [DX1004]
MBM29LV650UE@TSOP48 [DX1004]
MBM29LV651UE(REVERSE)@TSOP48 [DX1004]
MBM29LV651UE@TSOP48 [DX1004]　　MBM29LV652UE@FGBA63 [DX5041]
MBM29LV800B@PSOP44 [DX1014]　　MBM29LV800B@TSOP48 [DX1004]
MBM29LV800BA(REVERSE)@TSOP48 [DX1004]
MBM29LV800BA@FBGA48 [DX5039]　　MBM29LV800BA@PSOP44 [DX1014]
MBM29LV800BA@TSOP48 [DX1004]　　MBM29LV800BB@PSOP44 [DX1014]
MBM29LV800BB@TSOP48 [DX1004]
MBM29LV800BE(REVERSE)@TSOP48 [DX1004]
MBM29LV800BE@FBGA48 [DX5039]　　MBM29LV800BE@PSOP44 [DX1014]
MBM29LV800BE@TSOP48 [DX1004]　　MBM29LV800BT@PSOP44 [DX1014]
MBM29LV800BT@TSOP48 [DX1004]　　MBM29LV800T@PSOP44 [DX1014]
MBM29LV800T@TSOP48 [DX1004]
MBM29LV800TA(REVERSE)@TSOP48 [DX1004]
MBM29LV800TA@FBGA48 [DX5039]　　MBM29LV800TA@PSOP44 [DX1014]
MBM29LV800TA@TSOP48 [DX1004]
MBM29LV800TE(REVERSE)@TSOP48 [DX1004]
MBM29LV800TE@FBGA48 [DX5039]　　MBM29LV800TE@PSOP44 [DX1014]
MBM29LV800TE@TSOP48 [DX1004]　　MBM29PDS323B@FBGA63 [DX5047]
MBM29PDS323T@FBGA63 [DX5047]　　MBM29PL12LM@TSOP56 [DX1011]
MBM29PL160BD@PSOP44 [DX1014]　　MBM29PL160BD@TSOP48 [DX1004]
MBM29PL160TD@PSOP44 [DX1014]　　MBM29PL160TD@TSOP48 [DX1004]
MBM29PL32BM@FBGA48 [DX5002]　　MBM29PL32BM@TSOP48 [DX1004]
MBM29PL32TM@FBGA48 [DX5002]　　MBM29PL32TM@TSOP48 [DX1004]
MBM29PL64LM@TSOP48 [DX1004]　　MBM29PL64LM@TSOP56 [DX1011]
MBM29PL65LM@TSOP48 [DX1004]　　MBM29QM12DH@FBGA80 [DX5001]
MBM29QM12DH@TSOP56 [DX1011]
MBM29SL160BD(REVERSE)@TSOP48 [DX1004]
MBM29SL160BD@FBGA48 [DX5022]　　MBM29SL160BD@TSOP48 [DX1004]
MBM29SL160TD(REVERSE)@TSOP48 [DX1004]
MBM29SL160TD@FBGA48 [DX5022]　　MBM29SL160TD@TSOP48 [DX1004]
MBM29SL800BD(REVERSE)@TSOP48 [DX1004]
MBM29SL800BD@FBGA48 [DX5022]　　MBM29SL800BD@TSOP48 [DX1004]

MBM29SL800BE@FBGA48 [DX5043]
MBM29SL800TD(REVERSE)@TSOP48 [DX1004]
MBM29SL800TD@FBGA48 [DX5002]
MBM29SL800TD@TSOP48 [DX1004]
MBM29SL800TE@FBGA48 [DX5043]
MBM29XL12DF@SSOP90 [DX1083]
MSP29LV128@PSOP44 [DX1014]
MSP29LV128N@PSOP44 [DX1014]
MSP29LV256@TSOP56 [DX1057]
MSP29LV512@SSOP70 [DX1057]
MSP29LV512@TSOP56 [DX1057]
MSP55LV650@PSOP44(slow) [DX1014]
MSP64LV100@FBGA54 [DX5004]
MSP64LV200@FBGA54 [DX5004]
MSP64LV202@FBGA54 [DX5004]

BPROM

MB7121E/H [DX0001]
MB7121E/H@PLCC20 [DX2020]
MB7121L [DX0001]
MB7121L@PLCC20 [DX2020]
MB7122E/H/Y [DX0001]
MB7122E/H/Y@PLCC20 [DX2020]
MB7122L [DX0001]
MB7122L@PLCC20 [DX2020]
MB7123E/H [DX0001]
MB7123E/H@PLCC20 [DX2020]
MB7123L [DX0001]
MB7123L@PLCC20 [DX2020]
MB7124E/H/Y [DX0001]
MB7124E/H/Y@PLCC20 [DX2020]
MB7124L [DX0001]
MB7124L@PLCC20 [DX2020]
MB7127E/H [DX0001]
MB7127E/H@PLCC28 [DX2028]
MB7127L [DX0001]
MB7127L@PLCC28 [DX2028]
MB7128E/H/Y [DX0001]
MB7128E/H/Y@PLCC28 [DX2028]
MB7128L [DX0001]
MB7128L@PLCC28 [DX2028]
MB7131E/H/L [DX0001]
MB7131E/H/L@PLCC28 [DX2028]
MB7131E-SK [DX0001]
MB7131E-SK@PLCC28 [DX2028]
MB7131H-SK [DX0001]
MB7131H-SK@PLCC28 [DX2028]
MB7131L-SK [DX0001]
MB7131L-SK@PLCC28 [DX2028]
MB7132E/H/Y/L [DX0001]
MB7132E/H/Y/L@PLCC28 [DX2028]
MB7132E-SK [DX0001]
MB7132E-SK@PLCC28 [DX2028]
MB7132H-SK [DX0001]
MB7132H-SK@PLCC28 [DX2028]
MB7132L-SK [DX0001]
MB7132L-SK@PLCC28 [DX2028]
MB7132Y-SK [DX0001]
MB7132Y-SK@PLCC28 [DX2028]
MB7133E/H [DX0001]
MB7133E/H@PLCC28 [DX2028]
MB7134E/H/Y [DX0001]
MB7134E/H/Y@PLCC28 [DX2028]
MB7137E/H [DX0001]
MB7137E/H@PLCC28 [DX2028]
MB7137E-SK [DX0001]
MB7137E-SK@PLCC28 [DX2028]
MB7137H-SK [DX0001]
MB7137H-SK@PLCC28 [DX2028]
MB7137L [DX0001]
MB7138E/H/Y [DX0001]
MB7138E/H/Y@PLCC28 [DX2028]
MB7138E-SK [DX0001]
MB7138E-SK@PLCC28 [DX2028]
MB7138H-SK [DX0001]
MB7138H-SK@PLCC28 [DX2028]
MB7138L [DX0001]
MB7138Y-SK [DX0001]
MB7138Y-SK@PLCC28 [DX2028]
MB7142E/H [DX0001]
MB7142E/H@PLCC28 [DX2028]
MB71A38 [DX0001]

DRAM & SRAM

MB81C78A [DX0001]
MB81C78A@SOIC28

MICROCONTROLLER

MB85RS256 [DX0001]
MB85RS256@SOIC14 [DX1033]
MB85RS256@SOIC8 [DX1045]
MB85RS256A [DX0001]
MB85RS256A@SOIC14 [DX1033]
MB85RS256A@SOIC8 [DX1045]
MB89F202@SDIP32 [DX0032]
MB89F202@SSOP34 [DX1027]
MB89F202A@SDIP32 [DX0032]
MB89F202A@SSOP34 [DX1027]
MB89F202R@QFP32 [DX3001]
MB89F202R@SDIP32 [DX0032]
MB89F202R@SSOP34 [DX1027]
MB89F202RA@QFP32 [DX3001]
MB89F202RA@SDIP32 [DX0032]
MB89F202RA@SSOP34 [DX1027]
MB89F482AS@LQFP44 [DX3002]
MB89F482AS@SDIP42 [DX0042]
MB89F482AW@LQFP44 [DX3002]
MB89F482AW@SDIP42 [DX0042]
MB89F482HS@LQFP44 [DX3002]
MB89F482HS@SDIP42 [DX0042]
MB89F482HW@LQFP44 [DX3002]
MB89F482HW@SDIP42 [DX0042]
MB89F497APF@QFP80 [DX3020]
MB89F497APFV@LQFP80 [DX3017]
MB89F497PF@QFP80 [DX3020]
MB89F497PFV@LQFP80 [DX3017]
MB89F499PF@LQFP100 [DX3023]
MB89F499PFV@LQFP100 [DX3043]
MB89F538@SDIP64 [DX0064]
MB89F538-101PF@TQFP64 [DX3011]
MB89F538-101PFM@TQFP64 [DX3012]
MB89F538-201PF@TQFP64 [DX3011]
MB89F538-201PFM@TQFP64 [DX3012]
MB89F538L@SDIP64 [DX0064]
MB89F538L-101PF@TQFP64 [DX3011]
MB89F538L-101PFM@TQFP64 [DX3012]
MB89F538L-201PF@TQFP64 [DX3011]
MB89F538L-201PFM@TQFP64 [DX3012]
MB89P131APFM@QFP48 [DX3006]
MB89P131PFM@QFP48 [DX3006]
MB89P133APFM@QFP48 [DX3006]
MB89P133PFM@QFP48 [DX3006]
MB89P135APFM@QFP48 [DX3006]
MB89P135PFM@QFP48 [DX3006]
MB89P165-101(PF)@QFP80 [DX3019]
MB89P165-101(PFM)@LQFP80 [DX3017]
MB89P165-101(PFV)@LQFP80 [DX3016]
MB89P165-102(PF)@QFP80 [DX3019]
MB89P165-102(PFM)@LQFP80 [DX3017]
MB89P165-102(PFV)@LQFP80 [DX3016]
MB89P165-103(PF)@QFP80 [DX3019]
MB89P165-103(PFM)@LQFP80 [DX3017]
MB89P165-103(PFV)@LQFP80 [DX3016]
MB89P165-104(PF)@QFP80 [DX3019]
MB89P165-104(PFM)@LQFP80 [DX3017]
MB89P165-104(PFV)@LQFP80 [DX3016]
MB89P165-105(PF)@QFP80 [DX3019]
MB89P165-105(PFM)@LQFP80 [DX3017]
MB89P165-105(PFV)@LQFP80 [DX3016]
MB89P165-201(PF)@QFP80 [DX3019]
MB89P165-201(PFM)@LQFP80 [DX3017]
MB89P165-201(PFV)@LQFP80 [DX3016]

MB89P165-202(PF)@QFP80 [DX3019]
MB89P165-202(PFM)@LQFP80 [DX3017]
MB89P165-202(PFV)@LQFP80 [DX3016]
MB89P165-203(PF)@QFP80 [DX3019]
MB89P165-203(PFM)@LQFP80 [DX3017]
MB89P165-203(PFV)@LQFP80 [DX3016]
MB89P195 [DX0001]
MB89P195(F)@SOIC28 [DX1035]
MB89P195AP [DX0001]
MB89P195AP(F)@SOIC28 [DX1035]
MB89P195P [DX0001]
MB89P195P(F)@SOIC28 [DX1035]
MB89P475-101P-SH@SDIP48 [DX0048]
MB89P475-102P-SH@SDIP48 [DX0048]
MB89P475-201P-SH@SDIP48 [DX0048]
MB89P475-202P-SH@SDIP48 [DX0048]
MB89P485LPFM-101@TQFP64 [DX3012]
MB89P485LPFM-102@TQFP64 [DX3012]
MB89P485LPFM-103@TQFP64 [DX3012]
MB89P485LPFM-104@TQFP64 [DX3012]
MB89P485LPFV-101@TQFP64 [DX3011]
MB89P485LPFV-102@TQFP64 [DX3011]
MB89P485LPFV-103@TQFP64 [DX3011]
MB89P485LPFV-104@TQFP64 [DX3011]
MB89P485PFM-101@TQFP64 [DX3012]
MB89P485PFM-102@TQFP64 [DX3012]
MB89P485PFM-103@TQFP64 [DX3012]
MB89P485PFM-104@TQFP64 [DX3012]
MB89P485PFV-101@TQFP64 [DX3011]
MB89P485PFV-102@TQFP64 [DX3011]
MB89P485PFV-103@TQFP64 [DX3011]
MB89P485PFV-104@TQFP64 [DX3011]
MB89P538@LQFP64 [DX3064]
MB89P538@PQFP64 [DX3049]
MB89P538@SDIP64 [DX0064]
MB89P538L@LQFP64 [DX3064]
MB89P538L@PQFP64 [DX3049]
MB89P538L@SDIP64 [DX0064]
MB89P627@LQFP64 [DX3011]
MB89P627@QFP64 [DX3015]
MB89P627@SDIP64 [DX0064]
MB89P627@TQFP64 [DX3064]
MB89P627P@LQFP64 [DX3011]
MB89P627P@QFP64 [DX3015]
MB89P627P@SDIP64 [DX0064]
MB89P627P@TQFP64 [DX3064]
MB89P635@LQFP64 [DX3011]
MB89P635@QFP64 [DX3015]
MB89P635@SDIP64 [DX0064]
MB89P635@TQFP64 [DX3064]
MB89P635P@LQFP64 [DX3011]
MB89P635P@QFP64 [DX3015]
MB89P635P@SDIP64 [DX0064]
MB89P635P@TQFP64 [DX3064]
MB89P637@LQFP64 [DX3011]
MB89P637@QFP64 [DX3015]
MB89P637@SDIP64 [DX0064]
MB89P637@TQFP64 [DX3064]
MB89P637P@LQFP64 [DX3011]
MB89P637P@QFP64 [DX3015]
MB89P637P@SDIP64 [DX0064]
MB89P637P@TQFP64 [DX3064]
MB89P857@SDIP64 [DX0064]
MB89P857P@SDIP64 [DX0064]
MB89P867@QFP80 [DX3019]
MB89P935ACP [DX0001]
MB89P935ACP--G-SH@SDIP32 [DX0032]
MB89P935CP [DX0001]
MB89P935CP--G-SH@SDIP32 [DX0032]
MB90867A@LQFP100 [DX3023]
MB90867A@TQFP100 [DX3021]
MB90867AS@LQFP100 [DX3023]
MB90867AS@TQFP100 [DX3021]
MB90F036APMC@QFP120 [DX3028]
MB90F038APF [DX3022]
MB90F038APMC [DX3021]
MB90F038ASPF [DX3022]
MB90F038ASPMC [DX3021]
MB90F038CAPF [DX3022]
MB90F038CAPMC [DX3021]
MB90F038CASPF [DX3022]
MB90F038CASPMC [DX3021]
MB90F038CSPF [DX3022]
MB90F038CSPMC [DX3021]
MB90F038SPF [DX3022]
MB90F038SPMC [DX3021]
MB90F057@LQFP100 [DX3021]
MB90F057@QFP100 [DX3022]
MB90F334APFF@LQFP120 [DX3028]

MB90F334APMC@LQFP120 [DX3028]
MB90F342A@QFP100 [DX3023]
MB90F342AS@QFP100 [DX3023]
MB90F342CA@QFP100 [DX3023]
MB90F342CAS@QFP100 [DX3023]
MB90F343A@QFP100 [DX3023]
MB90F343AS@QFP100 [DX3023]
MB90F343CA@QFP100 [DX3023]
MB90F343CAS@QFP100 [DX3023]
MB90F345A@QFP100 [DX3023]
MB90F345AS@QFP100 [DX3023]
MB90F345CA@QFP100 [DX3023]
MB90F345CAS@QFP100 [DX3023]
MB90F346A@QFP100 [DX3023]
MB90F346AS@QFP100 [DX3023]
MB90F346CA@QFP100 [DX3023]
MB90F346CAS@QFP100 [DX3023]
MB90F347@QFP100 [DX3023]
MB90F347A@QFP100 [DX3023]
MB90F347AS@QFP100 [DX3023]
MB90F347C@QFP100 [DX3023]
MB90F347CA@QFP100 [DX3023]
MB90F347CAS@QFP100 [DX3023]
MB90F347CS@QFP100 [DX3023]
MB90F347S@QFP100 [DX3023]
MB90F349A@QFP100 [DX3023]
MB90F349AS@QFP100 [DX3023]
MB90F349CA@QFP100 [DX3023]
MB90F349CAS@QFP100 [DX3023]
MB90F352SPFM@LQFP64 [DX3012]
MB90F377@LQFP144 [DX3041]
MB90F387SPMT@LQFP48 [DX3047]
MB90F394H@LQFP120 [DX3028]
MB90F395H@LQFP120 [DX3028]
MB90F423GA@QFP100 [DX3023]
MB90F423GB@QFP100 [DX3023]
MB90F423GC@QFP100 [DX3023]
MB90F428GA@QFP100 [DX3023]
MB90F428GB@QFP100 [DX3023]
MB90F428GC@QFP100 [DX3023]
MB90F438BPFV@TQFP100 [DX3021]
MB90F438BSPFV@TQFP100 [DX3021]
MB90F438LPFV@TQFP100 [DX3021]
MB90F438LSPFV@TQFP100 [DX3021]
MB90F439BPF@TQFP100 [DX3023]
MB90F439BSPF@TQFP100 [DX3023]
MB90F439PFV@TQFP100 [DX3021]
MB90F439SPFV@TQFP100 [DX3021]
MB90F342A@LQFP100 [DX3021]
MB90F342AS@LQFP100 [DX3021]
MB90F342CA@LQFP100 [DX3021]
MB90F342CAS@LQFP100 [DX3021]
MB90F343A@LQFP100 [DX3021]
MB90F343AS@LQFP100 [DX3021]
MB90F343CA@LQFP100 [DX3021]
MB90F343CAS@LQFP100 [DX3021]
MB90F345A@LQFP100 [DX3021]
MB90F345AS@LQFP100 [DX3021]
MB90F345CA@LQFP100 [DX3021]
MB90F345CAS@LQFP100 [DX3021]
MB90F346A@LQFP100 [DX3021]
MB90F346AS@LQFP100 [DX3021]
MB90F346CA@LQFP100 [DX3021]
MB90F346CAS@LQFP100 [DX3021]
MB90F347@LQFP100 [DX3021]
MB90F347A@LQFP100 [DX3021]
MB90F347AS@LQFP100 [DX3021]
MB90F347C@LQFP100 [DX3021]
MB90F347CA@LQFP100 [DX3021]
MB90F347CAS@LQFP100 [DX3021]
MB90F347CS@LQFP100 [DX3021]
MB90F347S@LQFP100 [DX3021]
MB90F349A@LQFP100 [DX3021]
MB90F349AS@LQFP100 [DX3021]
MB90F349CA@LQFP100 [DX3021]
MB90F349CAS@LQFP100 [DX3021]
MB90F352PFM@LQFP64 [DX3012]
MB90F372@LQFP144 [DX3041]
MB90F387PMT@LQFP48 [DX3047]
MB90F394@LQFP120 [DX3028]
MB90F395@LQFP120 [DX3028]
MB90F423GA@LQFP100 [DX3021]
MB90F423GB@LQFP100 [DX3021]
MB90F423GC@LQFP100 [DX3021]
MB90F428GA@LQFP100 [DX3021]
MB90F428GB@LQFP100 [DX3021]
MB90F428GC@LQFP100 [DX3021]
MB90F438BPF@LQFP100 [DX3023]
MB90F438BSPF@LQFP100 [DX3023]
MB90F438LPF@LQFP100 [DX3023]
MB90F438LSPF@LQFP100 [DX3023]
MB90F439BFV@LQFP100 [DX3021]
MB90F439BPFV@LQFP100 [DX3021]
MB90F439PF@LQFP100 [DX3023]
MB90F439SPF@LQFP100 [DX3023]
MB90F455PMT@LQFP48 [DX3007]

MB90F455SPMT@LQFP48 [DX3007]
MB90F456PMT@LQFP48 [DX3007]
MB90F456SPMT@LQFP48 [DX3007]
MB90F457PMT@LQFP48 [DX3007]
MB90F457SPMT@LQFP48 [DX3007]
MB90F462AP@SDIP64 [DX0064]
MB90F462APF@QFP64 [DX3049]
MB90F462APFM@LQFP64 [DX3012]
MB90F462P@SDIP64 [DX0064]
MB90F462PF@QFP64 [DX3049]
MB90F462PFM@LQFP64 [DX3012]
MB90F463AP@SDIP64 [DX0064]
MB90F463APF@QFP64 [DX3049]
MB90F463APFM@LQFP64 [DX3012]
MB90F474HPF@LQFP100 [DX3023]
MB90F474HPFV@QFP100 [DX3021]
MB90F474LPF@LQFP100 [DX3023]
MB90F474LPFV@QFP100 [DX3021]
MB90F481PF@LQFP100 [DX3023]
MB90F481PFV@TQFP100 [DX3021]
MB90F482PF@LQFP100 [DX3023]
MB90F482PFV@TQFP100 [DX3021]
MB90F488BPF@LQFP100 [DX3023]
MB90F488BPFV@TQFP100 [DX3021]
MB90F488PF@LQFP100 [DX3023]
MB90F488PFV@TQFP100 [DX3021]
MB90F489BPF@LQFP100 [DX3023]
MB90F489BPFV@TQFP100 [DX3021]
MB90F489PF@LQFP100 [DX3023]
MB90F489PFV@TQFP100 [DX3021]
MB90F497G@LQFP64 [DX3012]
MB90F497G@QFP64 [DX3015]
MB90F498G@LQFP64 [DX3012]
MB90F498G@QFP64 [DX3015]
MB90F523PFF@LQFP120 [DX3030]
MB90F523PFV@QFP120 [DX3028]
MB90F543GPF@LQFP100 [DX3023]
MB90F543GPFV@TQFP100 [DX3043]
MB90F543GSPF@LQFP100 [DX3023]
MB90F543GSPFV@TQFP100 [DX3043]
MB90F543PF@LQFP100 [DX3023]
MB90F543PF@LQFP100(*) [DX3023]
MB90F543PFV@TQFP100 [DX3043]
MB90F546GPF@LQFP100 [DX3023]
MB90F546GPFV@TQFP100 [DX3043]
MB90F546GSPF@LQFP100 [DX3023]
MB90F546GSPFV@TQFP100 [DX3043]
MB90F548GPF@LQFP100 [DX3023]
MB90F548GPFV@TQFP100 [DX3043]
MB90F548GSPF@LQFP100 [DX3023]
MB90F548GSPFV@TQFP100 [DX3043]
MB90F549GPF@LQFP100 [DX3023]
MB90F549GPFV@TQFP100 [DX3043]
MB90F549GSPF@LQFP100 [DX3023]
MB90F549GSPFV@TQFP100 [DX3043]
MB90F549PF@LQFP100 [DX3023]
MB90F549PFV@TQFP100 [DX3043]
MB90F553APF@QFP100 [DX3023]
MB90F553APFV@LQFP100 [DX3043]
MB90F553PF@QFP100 [DX3023]
MB90F553PFV@LQFP100 [DX3043]
MB90F562@LQFP64 [DX3012]
MB90F562@QFP64 [DX3015]
MB90F562@SDIP64 [DX0064]
MB90F562B@LQFP64 [DX3012]
MB90F562B@QFP64 [DX3015]
MB90F562B@SDIP64 [DX0064]
MB90F568@LQFP64 [DX3012]
MB90F568@QFP64 [DX3015]
MB90F568G@LQFP64 [DX3012]
MB90F568G@QFP64 [DX3015]
MB90F568T@LQFP64 [DX3012]
MB90F568T@QFP64 [DX3015]
MB90F583BPF [DX3077]
MB90F583BPFV [DX3021]
MB90F583CAPF@LQFP100 [DX3077]
MB90F583CAPFV@TQFP100 [DX3021]
MB90F583CBPF [DX3077]
MB90F583CBPFV [DX3021]
MB90F583CPF@LQFP100 [DX3077]
MB90F583CPFV@TQFP100 [DX3021]
MB90F590APF@QFP100 [DX3023]
MB90F590GPF@QFP100 [DX3023]
MB90F591APF@QFP100 [DX3023]
MB90F591GPF@QFP100 [DX3023]
MB90F592APF [DX3023]
MB90F592GPF [DX3023]
MB90F593APF [DX3023]
MB90F593GPF [DX3023]
MB90F594APF@QFP100 [DX3023]
MB90F594GPF@QFP100 [DX3023]
MB90F598GPF@PQFP100 [DX3023]
MB90F598PF@PQFP100 [DX3023]
MB90F653APF@PQFP100 [DX3023]
MB90F653APFV@LQFP100 [DX3043]
MB90F653ASPF@PQFP100 [DX3023]

MB90F653ASPFV@LQFP100 [DX3043]
MB90F653BPF@PQFP100 [DX3023]
MB90F653BPFV@LQFP100 [DX3043]
MB90F653BSPF@PQFP100 [DX3023]
MB90F653BSPFV@LQFP100 [DX3043]
MB90F654APF@PQFP100 [DX3023]
MB90F654APFV@LQFP100 [DX3043]
MB90F654ASPF@PQFP100 [DX3023]
MB90F654ASPFV@LQFP100 [DX3043]
MB90F654BPF@PQFP100 [DX3023]
MB90F654BPFV@LQFP100 [DX3043]
MB90F654BSPF@PQFP100 [DX3023]
MB90F654BSPFV@LQFP100 [DX3043]
MB90F822APF@PQFP80 [DX3019]
MB90F822APFM@LQFP80 [DX3017]
MB90F822APFV@LQFP80 [DX3016]
MB90F822PF@PQFP80 [DX3019]
MB90F822PFM@LQFP80 [DX3017]
MB90F822PFV@LQFP80 [DX3016]
MB90F823APF@PQFP80 [DX3019]
MB90F823APFM@LQFP80 [DX3017]
MB90F823APFV@LQFP80 [DX3016]
MB90F823PF@PQFP80 [DX3019]
MB90F823PFM@LQFP80 [DX3017]
MB90F823PFV@LQFP80 [DX3016]
MB90F867A@LQFP100 [DX3023]
MB90F867A@TQFP100 [DX3021]
MB90F867AS@LQFP100 [DX3023]
MB90F867AS@TQFP100 [DX3021]
MB90F882@LQFP100 [DX3021]
MB90F882@QFP100 [DX3022]
MB90F884@LQFP100 [DX3021]
MB90F884@QFP100 [DX3022]
MB90F897PMT@LQFP48 [DX3047]
MB90F897SPMT@LQFP48 [DX3047]
MB90F927@LQFP100 [DX3021]
MB90F927@QFP100 [DX3023]
MB90F927S@LQFP100 [DX3021]
MB90F927S@QFP100 [DX3023]
MB90F947@LQFP100 [DX3021]
MB90F947@QFP100 [DX3023]
MB90F947S@LQFP100 [DX3021]
MB90F947S@QFP100 [DX3023]
MB90P663APFM@QFP64 [DX3012]
MB91F267NPMC-G@LQFP64 [DX3012]
MB91F267NPMC-GE1@LQFP64 [DX3012]
MB91F267NPMC-GS@LQFP64 [DX3012]
MB91F267NPMC-GSE1@LQFP64 [DX3012]
MB91F267PMC-G@LQFP64 [DX3012]
MB91F267PMC-GE1@LQFP64 [DX3012]
MB91F267PMC-GS@LQFP64 [DX3012]
MB91F267PMC-GSE1@LQFP64 [DX3012]
MB91F361GA@QFP208 [DX3078]
MB91F361GB@QFP208 [DX3078]
MB91F362GA@QFP208 [DX3078]
MB91F362GB@QFP208 [DX3078]
MB91F365GB@LQFP120 [DX3028]
MB91F366GB@LQFP120 [DX3028]
MB91F367GB@LQFP120 [DX3028]
MB91F368GB@LQFP120 [DX3028]
MB91F376GB@LQFP120 [DX3028]
MB91F463AA [DX3035]
MB91F463AB [DX3035]
MB91F463CA [DX3035]
MB91F463CB [DX3035]
MB91F464AA@LQFP100 [DX3021]
MB91F464AB@LQFP100 [DX3021]
MB91F465AA [DX3035]
MB91F465AB [DX3035]
MB91F465CA [DX3035]
MB91F465CB [DX3035]
MB91F467BA [DX3035]
MB91F467BB [DX3035]
MB91F467BC [DX3035]
MB91F467CA [DX3035]
MB91F467CB [DX3035]
MB91F467CC [DX3035]
MB91F475@LQFP144 [DX3034]
MB91F478@LQFP144 [DX3034]
MB91F479@LQFP144 [DX3034]
MB91F482@LQFP100 [DX3021]
MB91F482@QFP100 [DX3023]
MB91F486@LQFP100 [DX3021]
MB91F486@QFP100 [DX3023]
MB91F487@LQFP100 [DX3021]
MB91F487@QFP100 [DX3023]
MB91F492(M23)@LQFP64 [DX3064]
MB91F492(M24)@LQFP64 [DX3011]
MB91F59ACHPB [DX5263]
MB91F59ACHSPB [DX5263]
MB91F59ACPB [DX5263]
MB91F59ACSPB [DX5263]
MB91F59BCHPB [DX5263]
MB91F59BCHSPB [DX5263]

MB91F59BCPB [DX5263]
MB91F59BCSPB [DX5263]
MB91F662@LQFP120 [DX3028]
MB95F012KP [DX0032]
MB95F012KPF [DX1033]
MB95F012KPFT [DX1000]
MB95F012KWQN [DX4015]
MB95F013KP [DX0032]
MB95F013KPF [DX3001]
MB95F013KWQN [DX4015]
MB95F014EPMC1 [DX3011]
MB95F014EPMC2 [DX3012]
MB95F104AJSPFM@QFP64 [DX3012]
MB95F104AJSPFV@QFP64 [DX3011]
MB95F104AJWPFM@QFP64 [DX3012]
MB95F104AJWPFV@QFP64 [DX3011]
MB95F104AMSPFM@QFP64 [DX3012]
MB95F104AMSPFV@QFP64 [DX3011]
MB95F104AMWPFM@QFP64 [DX3012]
MB95F104AMWPFV@QFP64 [DX3011]
MB95F104ANSPFM@QFP64 [DX3012]
MB95F104ANSPFV@QFP64 [DX3011]
MB95F104ANWPFM@QFP64 [DX3012]
MB95F104ANWPFV@QFP64 [DX3011]
MB95F104BJSPFM@QFP64 [DX3012]
MB95F104BJSPFV@QFP64 [DX3011]
MB95F104BJWPFM@QFP64 [DX3012]
MB95F104BJWPFV@QFP64 [DX3011]
MB95F104BMSPFM@QFP64 [DX3012]
MB95F104BMSPFV@QFP64 [DX3011]
MB95F104BMWPFM@QFP64 [DX3012]
MB95F104BMWPFV@QFP64 [DX3011]
MB95F104BNSPFM@QFP64 [DX3012]
MB95F104BNSPFV@QFP64 [DX3011]
MB95F104BNWPFM@QFP64 [DX3012]
MB95F104BNWPFV@QFP64 [DX3011]
MB95F106AJSPFM@QFP64 [DX3012]
MB95F106AJSPFV@QFP64 [DX3011]
MB95F106AJWPFM@QFP64 [DX3012]
MB95F106AJWPFV@QFP64 [DX3011]
MB95F106AMSPFM@QFP64 [DX3012]
MB95F106AMSPFV@QFP64 [DX3011]
MB95F106AMWPFM@QFP64 [DX3012]
MB95F106AMWPFV@QFP64 [DX3011]
MB95F106ANSPFM@QFP64 [DX3012]
MB95F106ANSPFV@QFP64 [DX3011]
MB95F106ANWPFM@QFP64 [DX3012]
MB95F106ANWPFV@QFP64 [DX3011]
MB95F106BJSPFM@QFP64 [DX3012]
MB95F106BJSPFV@QFP64 [DX3011]
MB95F106BJWPFM@QFP64 [DX3012]
MB95F106BJWPFV@QFP64 [DX3011]
MB95F106BMSPFM@QFP64 [DX3012]
MB95F106BMSPFV@QFP64 [DX3011]
MB95F106BMWPFM@QFP64 [DX3012]
MB95F106BMWPFV@QFP64 [DX3011]
MB95F106BNSPFM@QFP64 [DX3012]
MB95F106BNSPFV@QFP64 [DX3011]
MB95F106BNWPFM@QFP64 [DX3012]
MB95F106BNWPFV@QFP64 [DX3011]
MB95F108AHSPFM@LQFP64 [DX3012]
MB95F108AHSPFV@LQFP64 [DX3011]
MB95F108AHWPFM@LQFP64 [DX3012]
MB95F108AHWPFV@LQFP64 [DX3011]
MB95F108AJSM@LQFP64 [DX3012]
MB95F108AJSPFM@QFP64 [DX3012]
MB95F108AJSPFV@QFP64 [DX3011]
MB95F108AJSV@LQFP64 [DX3012]
MB95F108AJWM@LQFP64 [DX3012]
MB95F108AJWPFM@QFP64 [DX3012]
MB95F108AJWPFV@QFP64 [DX3011]
MB95F108AJWV@LQFP64 [DX3012]
MB95F108AKSPFM@LQFP64 [DX3012]
MB95F108AKSPFV@LQFP64 [DX3011]
MB95F108AKWPFM@LQFP64 [DX3012]
MB95F108AKWPFV@LQFP64 [DX3011]
MB95F108AMM@LQFP64 [DX3012]
MB95F108AMSPFM@QFP64 [DX3012]
MB95F108AMSPFV@QFP64 [DX3011]
MB95F108AMV@LQFP64 [DX3011]
MB95F108AMWM@LQFP64 [DX3012]
MB95F108AMWPFM@QFP64 [DX3012]
MB95F108AMWPFV@QFP64 [DX3011]
MB95F108AMWV@LQFP64 [DX3012]
MB95F108ANSM@LQFP64 [DX3012]
MB95F108ANSPFM@QFP64 [DX3012]
MB95F108ANSPFV@QFP64 [DX3011]
MB95F108ANSV@LQFP64 [DX3012]
MB95F108ANWM@LQFP64 [DX3012]
MB95F108ANWPFM@QFP64 [DX3012]
MB95F108ANWPFV@QFP64 [DX3011]
MB95F108ANWV@LQFP64 [DX3012]
MB95F108ASPFM@LQFP64 [DX3012]
MB95F108ASPFV@LQFP64 [DX3011]
MB95F108ATSPFM@LQFP64 [DX3012]
MB95F108ATSPFV@LQFP64 [DX3011]

MB95F108ATWPFM@LQFP64 [DX3012]
MB95F108ATWPFV@LQFP64 [DX3011]
MB95F108AWPFM@LQFP64 [DX3012]
MB95F108AWPFV@LQFP64 [DX3011]
MB95F108BHSPFM@LQFP64 [DX3012]
MB95F108BHSPFV@LQFP64 [DX3011]
MB95F108BHWPFM@LQFP64 [DX3012]
MB95F108BHWPFV@LQFP64 [DX3011]
MB95F108BJSM@LQFP64 [DX3012]
MB95F108BJSPFM@QFP64 [DX3012]
MB95F108BJSPFV@QFP64 [DX3011]
MB95F108BJSV@LQFP64 [DX3012]
MB95F108BJWM@LQFP64 [DX3012]
MB95F108BJWPFM@QFP64 [DX3012]
MB95F108BJWPFV@QFP64 [DX3011]
MB95F108BJWV@LQFP64 [DX3012]
MB95F108BKSPFM@LQFP64 [DX3012]
MB95F108BKSPFV@LQFP64 [DX3011]
MB95F108BKWPFM@LQFP64 [DX3012]
MB95F108BKWPFV@LQFP64 [DX3011]
MB95F108BMM@LQFP64 [DX3012]
MB95F108BMSPFM@QFP64 [DX3012]
MB95F108BMSPFV@QFP64 [DX3011]
MB95F108BMV@LQFP64 [DX3011]
MB95F108BMWM@LQFP64 [DX3012]
MB95F108BMWPFM@QFP64 [DX3012]
MB95F108BMWPFV@QFP64 [DX3011]
MB95F108BMWV@LQFP64 [DX3012]
MB95F108BNSM@LQFP64 [DX3012]
MB95F108BNSPFM@QFP64 [DX3012]
MB95F108BNSPFV@QFP64 [DX3011]
MB95F108BNSV@LQFP64 [DX3012]
MB95F108BNWM@LQFP64 [DX3012]
MB95F108BNWPFM@QFP64 [DX3012]
MB95F108BNWPFV@QFP64 [DX3011]
MB95F108BNWV@LQFP64 [DX3012]
MB95F108BSPFM@LQFP64 [DX3012]
MB95F108BSPFV@LQFP64 [DX3011]
MB95F108BTSPFM@LQFP64 [DX3012]
MB95F108BTSPFV@LQFP64 [DX3011]
MB95F108BTWPFM@LQFP64 [DX3012]
MB95F108BTWPFV@LQFP64 [DX3011]
MB95F108BWPFM@LQFP64 [DX3012]
MB95F108BWPFV@LQFP64 [DX3011]
MB95F108HSPFM@LQFP64 [DX3012]
MB95F108HSPFV@LQFP64 [DX3011]
MB95F108HWPFM@LQFP64 [DX3012]
MB95F108HWPFV@LQFP64 [DX3011]
MB95F114JAS@LQFP52 [DX3010]
MB95F114JAW@LQFP52 [DX3010]
MB95F114JS@LQFP52 [DX3010]
MB95F114JW@LQFP52 [DX3010]
MB95F114MAS@LQFP52 [DX3010]
MB95F114MAW@LQFP52 [DX3010]
MB95F114MS@LQFP52 [DX3010]
MB95F114MW@LQFP52 [DX3010]
MB95F114NAS@LQFP52 [DX3010]
MB95F114NAW@LQFP52 [DX3010]
MB95F114NS@LQFP52 [DX3010]
MB95F114NW@LQFP52 [DX3010]
MB95F116JAS@LQFP52 [DX3010]
MB95F116JAW@LQFP52 [DX3010]
MB95F116JS@LQFP52 [DX3010]
MB95F116JW@LQFP52 [DX3010]
MB95F116MAS@LQFP52 [DX3010]
MB95F116MAW@LQFP52 [DX3010]
MB95F116MS@LQFP52 [DX3010]
MB95F116MW@LQFP52 [DX3010]
MB95F116NAS@LQFP52 [DX3010]
MB95F116NAS@LQFP52(60K) [DX3010]
MB95F116NAW@LQFP52 [DX3010]
MB95F116NS@LQFP52 [DX3010]
MB95F116NW@LQFP52 [DX3010]
MB95F118AS@LQFP48 [DX3047]
MB95F118AS@LQFP52 [DX3010]
MB95F118AW@LQFP48 [DX3047]
MB95F118AW@LQFP52 [DX3010]
MB95F118BS@LQFP48 [DX3047]
MB95F118BS@LQFP52 [DX3010]
MB95F118BW@LQFP48 [DX3047]
MB95F118BW@LQFP52 [DX3010]
MB95F118HS@LQFP48 [DX3047]
MB95F118HS@LQFP52 [DX3010]
MB95F118HW@LQFP48 [DX3047]
MB95F118HW@LQFP52 [DX3010]
MB95F118MS@LQFP48 [DX3047]
MB95F118MS@LQFP52 [DX3010]
MB95F118MW@LQFP48 [DX3047]
MB95F118MW@LQFP52 [DX3010]
MB95F118NS@LQFP48 [DX3047]
MB95F118NS@LQFP52 [DX3010]
MB95F118NW@LQFP48 [DX3047]
MB95F118NW@LQFP52 [DX3010]
MB95F118TS@LQFP48 [DX3047]
MB95F118TS@LQFP52 [DX3010]
MB95F118TW@LQFP48 [DX3047]

MB95F118TW@LQFP52 [DX3010]
MB95F128D@QFP100 [DX3022]
MB95F128E@QFP100 [DX3022]
MB95F128H@QFP100 [DX3022]
MB95F128J@QFP100 [DX3022]
MB95F128M@QFP100 [DX3022]
MB95F128N@QFP100 [DX3022]
MB95F128T@QFP100 [DX3022]
MB95F133HBW@SSOP30 [DX1027]
MB95F133HW@SOP28 [DX1035]
MB95F133JBW@SSOP30 [DX1027]
MB95F133JW@SOP28 [DX1035]
MB95F133MBW@SSOP30 [DX1027]
MB95F133MW@SOP28 [DX1035]
MB95F133NBW@SSOP30 [DX1027]
MB95F133NW@SOP28 [DX1035]
MB95F133TBW@SSOP30 [DX1027]
MB95F133TW@SOP28 [DX1035]
MB95F134HBW@SSOP30 [DX1027]
MB95F134HW@SOP28 [DX1035]
MB95F134JBW@SSOP30 [DX1027]
MB95F134JW@SOP28 [DX1035]
MB95F134MBW@SSOP30 [DX1027]
MB95F134MW@SOP28 [DX1035]
MB95F134NBW@SSOP30 [DX1027]
MB95F134NW@SOP28 [DX1035]
MB95F134TBW@SSOP30 [DX1027]
MB95F134TW@SOP28 [DX1035]
MB95F136HBW@SSOP30 [DX1027]
MB95F136HW@SOP28 [DX1035]
MB95F136JBW@SSOP30 [DX1027]
MB95F136JW@SOP28 [DX1035]
MB95F136KBW@SSOP30 [DX1027]
MB95F136KW@SOP28 [DX1035]
MB95F136MBW@SSOP30 [DX1027]
MB95F136MW@SOP28 [DX1035]
MB95F136NBW@SSOP30 [DX1027]
MB95F136NW@SOP28 [DX1035]
MB95F136TBW@SSOP30 [DX1027]
MB95F136TW@SOP28 [DX1035]
MB95F156MPMT@LQFP48 [DX3047]
MB95F156NPMT@LQFP48 [DX3047]
MB95F166DPMC1@LQFP64 [DX3011]
MB95F168JA1@LQFP64 [DX3012]
MB95F168JPMC1@LQFP64 [DX3011]
MB95F168MPMC1@LQFP64 [DX3011]
MB95F168NPMC1@LQFP64 [DX3011]
MB95F176JSPMC1@LQFP64 [DX3011]
MB95F128D@LQFP100 [DX3043]
MB95F128E@LQFP100 [DX3043]
MB95F128H@LQFP100 [DX3043]
MB95F128J@LQFP100 [DX3043]
MB95F128M@LQFP100 [DX3043]
MB95F128N@LQFP100 [DX3043]
MB95F128T@LQFP100 [DX3043]
MB95F133HBS@SSOP30 [DX1027]
MB95F133HS@SOP28 [DX1035]
MB95F133JBS@SSOP30 [DX1027]
MB95F133JS@SOP28 [DX1035]
MB95F133MBS@SSOP30 [DX1027]
MB95F133MS@SOP28 [DX1035]
MB95F133NBS@SSOP30 [DX1027]
MB95F133NS@SOP28 [DX1035]
MB95F133TBS@SSOP30 [DX1027]
MB95F133TS@SOP28 [DX1035]
MB95F134HBS@SSOP30 [DX1027]
MB95F134HS@SOP28 [DX1035]
MB95F134JBS@SSOP30 [DX1027]
MB95F134JS@SOP28 [DX1035]
MB95F134MBS@SSOP30 [DX1027]
MB95F134MS@SOP28 [DX1035]
MB95F134NBS@SSOP30 [DX1027]
MB95F134NS@SOP28 [DX1035]
MB95F134TBS@SSOP30 [DX1027]
MB95F134TS@SOP28 [DX1035]
MB95F136HBS@SSOP30 [DX1027]
MB95F136HS@SOP28 [DX1035]
MB95F136JBS@SSOP30 [DX1027]
MB95F136JS@SOP28 [DX1035]
MB95F136KBS@SSOP30 [DX1027]
MB95F136KS@SOP28 [DX1035]
MB95F136MBS@SSOP30 [DX1027]
MB95F136MS@SOP28 [DX1035]
MB95F136NBS@SSOP30 [DX1027]
MB95F136NS@SOP28 [DX1035]
MB95F136TBS@SSOP30 [DX1027]
MB95F136TS@SOP28 [DX1035]
MB95F156MPMC@LQFP52 [DX3010]
MB95F156NPMC@LQFP52 [DX3010]
MB95F166DPMC@LQFP64 [DX3012]
MB95F168JA@LQFP64 [DX3012]
MB95F168JPMC@LQFP64 [DX3011]
MB95F168MPMC@LQFP64 [DX3011]
MB95F168NPMC@LQFP64 [DX3011]
MB95F176JSPMC@LQFP64 [DX3012]
MB95F176JWPMC@LQFP64 [DX3012]

MB95F176JWPMC1@LQFP64 [DX3011]
MB95F188J@QFP80 [DX3016]
MB95F202HAPF@SOP20 [DX1078]
MB95F202HPF@SOP20 [DX1078]
MB95F202KAPF@SOP20 [DX1078]
MB95F202KPF@SOP20 [DX1078]
MB95F203HAPF@SOP20 [DX1078]
MB95F203HPF@SOP20 [DX1078]
MB95F203KAPF@SOP20 [DX1078]
MB95F203KPF@SOP20 [DX1078]
MB95F204HAPF@SOP20 [DX1078]
MB95F204HPF@SOP20 [DX1078]
MB95F204KAPF@SOP20 [DX1078]
MB95F204KPF@SOP20 [DX1078]
MB95F212HPH [DX0001]
MB95F212KPH [DX0001]
MB95F213HPH [DX0001]
MB95F213KPH [DX0001]
MB95F214HPH [DX0001]
MB95F214KPH [DX0001]
MB95F222HPH [DX0001]
MB95F222KPH [DX0001]
MB95F223HPH [DX0001]
MB95F223KPH [DX0001]
MB95F224HPH [DX0001]
MB95F224KPH [DX0001]
MB95F232HPF@SOP20 [DX1078]
MB95F232KPF@SOP20 [DX1078]
MB95F233HPF@SOP20 [DX1078]
MB95F233KPF@SOP20 [DX1078]
MB95F234HPF@SOP20 [DX1078]
MB95F234KPF@SOP20 [DX1078]
MB95F242HPF@SOP8 [DX1032]
MB95F242KPF@SOP8 [DX1032]
MB95F243HPF@SOP8 [DX1032]
MB95F243KPF@SOP8 [DX1032]
MB95F244HPF@SOP8 [DX1032]
MB95F244KPF@SOP8 [DX1032]
MB95F252HPF@SOP16 [DX1032]
MB95F252KPF@SOP16 [DX1032]
MB95F253HPF@SOP16 [DX1032]
MB95F253KPF@SOP16 [DX1032]
MB95F254HPF@SOP16 [DX1032]
MB95F254KPF@SOP16 [DX1032]
MB95F262HPF@SOP20 [DX1078]
MB95F262HPS@TSOP20 [DX1067]
MB95F262KP@SDIP24 [DX0032]
MB95F262KPFT [DX1067]
MB95F188@QFP80 [DX3016]
MB95F202HAP@SDIP24 [DX0032]
MB95F202HP@SDIP24 [DX0032]
MB95F202KAP@SDIP24 [DX0032]
MB95F202KP@SDIP24 [DX0032]
MB95F203HAP@SDIP24 [DX0032]
MB95F203HP@SDIP24 [DX0032]
MB95F203KAP@SDIP24 [DX0032]
MB95F203KP@SDIP24 [DX0032]
MB95F204HAP@SDIP24 [DX0032]
MB95F204HP@SDIP24 [DX0032]
MB95F204KAP@SDIP24 [DX0032]
MB95F204KP@SDIP24 [DX0032]
MB95F212HPF@SOP8 [DX1044]
MB95F212KPF@SOP8 [DX1044]
MB95F213HPF@SOP8 [DX1044]
MB95F213KPF@SOP8 [DX1044]
MB95F214HPF@SOP8 [DX1044]
MB95F214KPF@SOP8 [DX1044]
MB95F222HPF@SOP16 [DX1032]
MB95F222KPF@SOP16 [DX1032]
MB95F223HPF@SOP16 [DX1032]
MB95F223KPF@SOP16 [DX1032]
MB95F224HPF@SOP16 [DX1032]
MB95F224KPF@SOP16 [DX1032]
MB95F232HP@SDIP24 [DX0032]
MB95F232KP@SDIP24 [DX0032]
MB95F233HP@SDIP24 [DX0032]
MB95F233KP@SDIP24 [DX0032]
MB95F234HP@SDIP24 [DX0032]
MB95F234KP@SDIP24 [DX0032]
MB95F242HP [DX0001]
MB95F242KP [DX0001]
MB95F243HP [DX0001]
MB95F243KP [DX0001]
MB95F244HP [DX0001]
MB95F244KP [DX0001]
MB95F252HP [DX0001]
MB95F252KP [DX0001]
MB95F253HP [DX0001]
MB95F253KP [DX0001]
MB95F254HP [DX0001]
MB95F254KP [DX0001]
MB95F262HP@SDIP24 [DX0032]
MB95F262HPFT [DX1067]
MB95F262HWQN [DX4015]
MB95F262KPF@SOP20 [DX1078]
MB95F262KPS@TSOP20 [DX1067]

MB95F262KWQN [DX4015]
MB95F263HPF@SOP20 [DX1078]
MB95F263HPS@TSOP20 [DX1067]
MB95F263KP@SDIP24 [DX0032]
MB95F263KPFT [DX1067]
MB95F263KWQN [DX4015]
MB95F264HPF@SOP20 [DX1078]
MB95F264HPS@SSOP20 [DX1067]
MB95F264KP@SDIP24 [DX0032]
MB95F264KPFT [DX1067]
MB95F264KWQN [DX4015]
MB95F272HPF@SOP8 [DX1032]
MB95F272KPF@SOP8 [DX1032]
MB95F273HPF@SOP8 [DX1032]
MB95F273KPF@SOP8 [DX1032]
MB95F274HPF@SOP8 [DX1032]
MB95F274KPF@SOP8 [DX1032]
MB95F282HPF@SOP16 [DX1032]
MB95F282KP [DX0001]
MB95F282KWQN [DX4015]
MB95F283HPF@SOP16 [DX1032]
MB95F283KP [DX0001]
MB95F283KWQN [DX4015]
MB95F284HPF@SOP16 [DX1032]
MB95F284KP [DX0001]
MB95F284KWQN [DX4015]
MB95F314E@QFP80(Parallel) [DX3016]
MB95F314L@QFP80 [DX3016]
MB95F314L@QFP80(Parallel) [DX3016]
MB95F316E@QFP80 [DX3016]
MB95F316E@QFP80(Parallel) [DX3016]
MB95F316L@QFP80 [DX3016]
MB95F316L@QFP80(Parallel) [DX3016]
MB95F318E@QFP80 [DX3016]
MB95F318E@QFP80(Parallel) [DX3016]
MB95F318L@QFP80 [DX3016]
MB95F318L@QFP80(Parallel) [DX3016]
MB95F332HP@SDIP32 [DX0032]
MB95F332HP@SDIP32(Parallel) [DX0032]
MB95F332HPF@LQFP32 [DX3001]
MB95F332HPF@LQFP32(Parallel) [DX3001]
MB95F332HWQN [DX4015]
MB95F332HWQN@QFN32(Parallel) [DX4015]
MB95F332KP@SDIP32 [DX0032]
MB95F332KP@SDIP32(Parallel) [DX0032]
MB95F332KPF@LQFP32 [DX3001]
MB95F332KPF@LQFP32(Parallel) [DX3001]
MB95F332KWQN [DX4015]
MB95F263HP@SDIP24 [DX0032]
MB95F263HPFT [DX1067]
MB95F263HWQN [DX4015]
MB95F263KPF@SOP20 [DX1078]
MB95F263KPS@TSOP20 [DX1067]
MB95F264HP@SDIP24 [DX0032]
MB95F264HPFT [DX1067]
MB95F264HWQN [DX4015]
MB95F264KPF@SOP20 [DX1078]
MB95F264KPS@SSOP20 [DX1067]
MB95F272HP [DX0001]
MB95F272KP [DX0001]
MB95F273HP [DX0001]
MB95F273KP [DX0001]
MB95F274HP [DX0001]
MB95F274KP [DX0001]
MB95F282HP [DX0001]
MB95F282HWQN [DX4015]
MB95F282KPF@SOP16 [DX1032]
MB95F283HP [DX0001]
MB95F283HWQN [DX4015]
MB95F283KPF@SOP16 [DX1032]
MB95F284HP [DX0001]
MB95F284HWQN [DX4015]
MB95F284KPF@SOP16 [DX1032]
MB95F314E@QFP80 [DX3016]

MB95F332KWQN@QFN32(Parallel) [DX4015]
MB95F333HP@SDIP32 [DX0032]
MB95F333HP@SDIP32(Parallel) [DX0032]
MB95F333HPF@LQFP32 [DX3001]
MB95F333HPF@LQFP32(Parallel) [DX3001]
MB95F333HWQN [DX4015]
MB95F333HWQN@QFN32(Parallel) [DX4015]
MB95F333KP@SDIP32 [DX0032]
MB95F333KP@SDIP32(Parallel) [DX0032]
MB95F333KPF@LQFP32 [DX3001]
MB95F333KPF@LQFP32(Parallel) [DX3001]
MB95F333KWQN [DX4015]
MB95F333KWQN@QFN32(Parallel) [DX4015]
MB95F334HP@SDIP32 [DX0032]
MB95F334HP@SDIP32(Parallel) [DX0032]
MB95F334HPF@LQFP32 [DX3001]
MB95F334HPF@LQFP32(Parallel) [DX3001]
MB95F334HWQN [DX4015]
MB95F334HWQN@QFN32(Parallel) [DX4015]
MB95F334KP@SDIP32 [DX0032]
MB95F334KP@SDIP32(Parallel) [DX0032]
MB95F334KPF@LQFP32 [DX3001]
MB95F334KPF@LQFP32(Parallel) [DX3001]
MB95F334KWQN [DX4015]
MB95F334KWQN@QFN32(Parallel) [DX4015]
MB95F352E@QFP32(Parallel) [DX3001]
MB95F352E@SOIC24(Parallel) [DX1033]
MB95F352E@SSOP24(Parallel) [DX1001]
MB95F352L@QFP32(Parallel) [DX3001]
MB95F352L@SOIC24(Parallel) [DX1033]
MB95F352L@SSOP24(Parallel) [DX1001]
MB95F353E@QFP32(Parallel) [DX3001]
MB95F353E@SOIC24(Parallel) [DX1033]
MB95F353E@SSOP24(Parallel) [DX1001]
MB95F353L@QFP32(Parallel) [DX3001]
MB95F353L@SOIC24(Parallel) [DX1033]
MB95F353L@SSOP24(Parallel) [DX1001]
MB95F354E@QFP32(Parallel) [DX3001]
MB95F354E@SOIC24(Parallel) [DX1033]
MB95F354E@SSOP24(Parallel) [DX1001]
MB95F354L@QFP32(Parallel) [DX3001]
MB95F354L@SOIC24(Parallel) [DX1033]
MB95F354L@SSOP24(Parallel) [DX1001]
MB95F374E@LQFP64 [DX3057]
MB95F374E@LQFP64(Parallel) [DX3057]
MB95F374E@QFP64 [DX3064]
MB95F374E@QFP64(Parallel) [DX3064]
MB95F374L@LQFP64 [DX3057]

MB95F374L@LQFP64(Parallel) [DX3057]
MB95F374L@QFP64 [DX3064]
MB95F374L@QFP64(Parallel) [DX3064]
MB95F376E@LQFP64 [DX3057]
MB95F376E@LQFP64(Parallel) [DX3057]
MB95F376E@QFP64 [DX3064]
MB95F376E@QFP64(Parallel) [DX3064]
MB95F376L@LQFP64 [DX3057]
MB95F376L@LQFP64(Parallel) [DX3057]
MB95F376L@QFP64 [DX3064]
MB95F376L@QFP64(Parallel) [DX3064]
MB95F378E@LQFP64 [DX3057]
MB95F378E@LQFP64(Parallel) [DX3057]
MB95F378E@QFP64 [DX3064]
MB95F378E@QFP64(Parallel) [DX3064]
MB95F378L@LQFP64 [DX3057]
MB95F378L@LQFP64(Parallel) [DX3057]
MB95F378L@QFP64 [DX3064]
MB95F378L@QFP64(Parallel) [DX3064]
MB95F394H@QFN48 [DX4021]
MB95F394H@QFN48(Parallel) [DX4021]
MB95F394H@QFP48 [DX3007]
MB95F394H@QFP48(Parallel) [DX3007]
MB95F394H@QFP52 [DX3010]
MB95F394H@QFP52(Parallel) [DX3010]
MB95F394K@QFN48 [DX4021]
MB95F394K@QFN48(Parallel) [DX4021]
MB95F394K@QFP48 [DX3007]
MB95F394K@QFP48(Parallel) [DX3007]
MB95F394K@QFP52 [DX3010]
MB95F394K@QFP52(Parallel) [DX3010]
MB95F396H@QFN48 [DX4021]
MB95F396H@QFN48(Parallel) [DX4021]
MB95F396H@QFP48 [DX3007]
MB95F396H@QFP48(Parallel) [DX3007]
MB95F396H@QFP52 [DX3010]
MB95F396H@QFP52(Parallel) [DX3010]
MB95F396K@QFN48 [DX4021]
MB95F396K@QFN48(Parallel) [DX4021]
MB95F396K@QFP48 [DX3007]
MB95F396K@QFP48(Parallel) [DX3007]
MB95F396K@QFP52 [DX3010]
MB95F396K@QFP52(Parallel) [DX3010]
MB95F398H@QFN48 [DX4021]
MB95F398H@QFN48(Parallel) [DX4021]
MB95F398H@QFP48 [DX3007]
MB95F398H@QFP48(Parallel) [DX3007]
MB95F398H@QFP52 [DX3010]

MB95F398H@QFP52(Parallel) [DX3010]
MB95F398K@QFN48 [DX4021]
MB95F398K@QFN48(Parallel) [DX4021]
MB95F398K@QFP48 [DX3007]
MB95F398K@QFP48(Parallel) [DX3007]
MB95F398K@QFP52 [DX3010]
MB95F398K@QFP52(Parallel) [DX3010]
MB95F414HPMC [DX3016] MB95F414KPMC [DX3016]
MB95F416HPMC [DX3016] MB95F416KPMC [DX3016]
MB95F418HPMC [DX3016] MB95F418KPMC [DX3016]
MB95F432HP@SDIP32(Parallel) [DX0032]
MB95F432HPF@LQFP32(Parallel) [DX3001]
MB95F432KP@SDIP32(Parallel) [DX0032]
MB95F432KPF@LQFP32(Parallel) [DX3001]
MB95F433HP@SDIP32(Parallel) [DX0032]
MB95F433HPF@LQFP32(Parallel) [DX3001]
MB95F433KP@SDIP32(Parallel) [DX0032]
MB95F433KPF@LQFP32(Parallel) [DX3001]
MB95F434HP@SDIP32(Parallel) [DX0032]
MB95F434HPF@LQFP32(Parallel) [DX3001]
MB95F434KP@SDIP32(Parallel) [DX0032]
MB95F434KPF@LQFP32(Parallel) [DX3001]
MB95F474HPMC1 [DX3011] MB95F474HPMC2 [DX3012]
MB95F474KPMC1 [DX3011] MB95F474KPMC2 [DX3012]
MB95F476HPMC1 [DX3011] MB95F476HPMC2 [DX3012]
MB95F476KPMC1 [DX3011] MB95F476KPMC2 [DX3012]
MB95F478HPMC1 [DX3011] MB95F478HPMC2 [DX3012]
MB95F478KPMC1 [DX3011] MB95F478KPMC2 [DX3012]
MB95F562HP [DX0032] MB95F562HPF [DX1033]
MB95F562HPFT [DX1000] MB95F562HPS [DX1000]
MB95F562HWQN [DX4015] MB95F562KP [DX0032]
MB95F562KPF [DX1033] MB95F562KPFT [DX1000]
MB95F562KPS [DX1000] MB95F562KWQN [DX4015]
MB95F563HP [DX0032] MB95F563HPF [DX1033]
MB95F563HPFT [DX1000] MB95F563HPS [DX1000]
MB95F563HWQN [DX4015] MB95F563KP [DX0032]
MB95F563KPF [DX1033] MB95F563KPFT [DX1000]
MB95F563KPS [DX1000] MB95F563KWQN [DX4015]
MB95F564HP [DX0032] MB95F564HPF [DX1033]
MB95F564HPFT [DX1000] MB95F564HPS [DX1000]
MB95F564HWQN [DX4015] MB95F564KP [DX0032]
MB95F564KPF [DX1033] MB95F564KPFT [DX1000]
MB95F564KPS [DX1000] MB95F564KWQN [DX4015]
MB95F572HP [DX0001] MB95F572HPF [DX1032]
MB95F572KP [DX0001] MB95F572KPF [DX1032]
MB95F573HP [DX0001] MB95F573HPF [DX1032]
MB95F573KP [DX0001] MB95F573KPF [DX1032]
MB95F574HP [DX0001] MB95F574HPF [DX1032]

MB95F574KP [DX0001]
MB95F574KPF [DX1032]
MB95F582HP [DX0001]
MB95F582HPF [DX1032]
MB95F582HWQN [DX4015]
MB95F582KP [DX0001]
MB95F582KPF [DX1032]
MB95F582KWQN [DX4015]
MB95F583HP [DX0001]
MB95F583HPF [DX1032]
MB95F583HWQN [DX4015]
MB95F583KP [DX0001]
MB95F583KPF [DX1032]
MB95F583KWQN [DX4015]
MB95F584HP [DX0001]
MB95F584HPF [DX1032]
MB95F584HWQN [DX4015]
MB95F584KP [DX0001]
MB95F584KPF [DX1032]
MB95F584KWQN [DX4015]
MB95F632HP [DX0032]
MB95F632HPF [DX3001-3]
MB95F632HWQN [DX4015]
MB95F632KP [DX0032]
MB95F632KPF [DX3001-3]
MB95F632KWQN [DX4015]
MB95F633HP [DX0032]
MB95F633HPF [DX3001-3]
MB95F633HWQN [DX4015]
MB95F633KP [DX0032]
MB95F633KPF [DX3001-3]
MB95F633KWQN [DX4015]
MB95F634HP [DX0032]
MB95F634HPF [DX3001-3]
MB95F634HWQN [DX4015]
MB95F634KP [DX0032]
MB95F634KPF [DX3001-3]
MB95F634KWQN [DX4015]
MB95F636HP [DX0032]
MB95F636HPF [DX3001-3]
MB95F636HWQN [DX4015]
MB95F636KP [DX0032]
MB95F636KPF [DX3001-3]
MB95F636KWQN [DX4015]
MB95F652E@QFN32 [DX4015]
MB95F652E@QFP32 [DX3001]
MB95F652E@SOIC24 [DX1033]
MB95F652E@SSOP24 [DX1001]
MB95F652L@QFN32 [DX4015]
MB95F652L@QFP32 [DX3001]
MB95F652L@SOIC24 [DX1033]
MB95F652L@SSOP24 [DX1001]
MB95F653E@QFN32 [DX4015]
MB95F653E@QFP32 [DX3001]
MB95F653E@SOIC24 [DX1033]
MB95F653E@SSOP24 [DX1001]
MB95F653L@QFN32 [DX4015]
MB95F653L@QFP32 [DX3001]
MB95F653L@SOIC24 [DX1033]
MB95F653L@SSOP24 [DX1001]
MB95F654E@QFN32 [DX4015]
MB95F654E@QFP32 [DX3001]
MB95F654E@SOIC24 [DX1033]
MB95F654E@SSOP24 [DX1001]
MB95F654L@QFN32 [DX4015]
MB95F654L@QFP32 [DX3001]
MB95F654L@SOIC24 [DX1033]
MB95F654L@SSOP24 [DX1001]
MB95F656E@QFN32 [DX4015]
MB95F656E@QFP32 [DX3001]
MB95F656E@SOIC24 [DX1033]
MB95F656E@SSOP24 [DX1001]
MB95F656L@QFN32 [DX4015]
MB95F656L@QFP32 [DX3001]
MB95F656L@SOIC24 [DX1033]
MB95F656L@SSOP24 [DX1001]
MB95F694K@QFN48 [DX4021]
MB95F694K@QFN48(parallel) [DX4021]
MB95F694K@QFP44 [DX3002-3]
MB95F694K@QFP48 [DX3007]
MB95F694K@QFP48(parallel) [DX3007]
MB95F694K@QFP52 [DX3010]
MB95F694K@QFP52(parallel) [DX3010]
MB95F696K@QFN48 [DX4021]
MB95F696K@QFN48(parallel) [DX4021]
MB95F696K@QFP44 [DX3002-3]
MB95F696K@QFP48 [DX3007]
MB95F696K@QFP48(parallel) [DX3007]

MB95F696K@QFP52 [DX3010]
MB95F696K@QFP52(parallel) [DX3010]
MB95F698K@QFN48 [DX4021]
MB95F698K@QFN48(parallel) [DX4021]
MB95F698K@QFP44 [DX3002-3]
MB95F698K@QFP48 [DX3007]
MB95F698K@QFP48(parallel) [DX3007]
MB95F698K@QFP52 [DX3010]
MB95F698K@QFP52(parallel) [DX3010]
MB95F714EPMC [DX3016]
MB95F714LPMC [DX3016]
MB95F716EPMC [DX3016]
MB95F716LPMC [DX3016]
MB95F718EPMC [DX3016]
MB95F718LPMC [DX3016]
MB95F774EPMC1 [DX3011]
MB95F774EPMC2 [DX3012]
MB95F774LPMC1 [DX3011]
MB95F774LPMC2 [DX3012]
MB95F776EPMC1 [DX3011]
MB95F776EPMC2 [DX3012]
MB95F776LPMC1 [DX3011]
MB95F776LPMC2 [DX3012]
MB95F778EPMC1 [DX3011]
MB95F778EPMC2 [DX3012]
MB95F778LPMC1 [DX3011]
MB95F778LPMC2 [DX3012]
MB95F814EPMC [DX3012-1]
MB95F814EPMC1 [DX3057-12]
MB95F814KPMC [DX3012-1]
MB95F814KPMC1 [DX3057-12]
MB95F814LPMC [DX3012-1]
MB95F814LPMC1 [DX3057-12]
MB95F816EPMC [DX3012-1]
MB95F816EPMC1 [DX3057-12]
MB95F816KPMC [DX3012-1]
MB95F816KPMC1 [DX3057-12]
MB95F816LPMC [DX3012-1]
MB95F816LPMC1 [DX3057-12]
MB95F818EPMC [DX3012-1]
MB95F818EPMC1 [DX3057-12]
MB95F818KPMC [DX3012-1]
MB95F818KPMC1 [DX3057-12]
MB95F818LPMC [DX3012-1]
MB95F818LPMC1 [DX3057-12]
MB95F856KPF [DX3001]
MB95F856KPFT [DX3001]
MB95F866KPMC [DX3001]
MB95F876K@QFP48 [DX3007]
MB95F876K@QFP48(parallel) [DX3007]
MB95F876K@QFP52 [DX3010]
MB95F876K@QFP52(parallel) [DX3010]
MB95R202HAP@SDIP24 [DX0032]
MB95R202HAPF@SOP20 [DX1033]
MB95R202HP@SDIP24 [DX0032]
MB95R202HPF@SOP20 [DX1033]
MB95R202KAP@SDIP24 [DX0032]
MB95R202KAPF@SOP20 [DX1033]
MB95R202KP@SDIP24 [DX0032]
MB95R202KPF@SOP20 [DX1033]
MB95R203HAP@SDIP24 [DX0032]
MB95R203HAPF@SOP20 [DX1033]
MB95R203HP@SDIP24 [DX0032]
MB95R203HPF@SOP20 [DX1033]
MB95R203KAP@SDIP24 [DX0032]
MB95R203KAPF@SOP20 [DX1033]
MB95R203KP@SDIP24 [DX0032]
MB95R203KPF@SOP20 [DX1033]
MB95R204HAP@SDIP24 [DX0032]
MB95R204HAPF@SOP20 [DX1033]
MB95R204HP@SDIP24 [DX0032]
MB95R204HPF@SOP20 [DX1033]
MB95R204KAP@SDIP24 [DX0032]
MB95R204KAPF@SOP20 [DX1033]
MB95R204KP@SDIP24 [DX0032]
MB95R204KPF@SOP20 [DX1033]
MB95R212HPF@SOP8 [DX1044]
MB95R212HPH [DX0001]
MB95R212KPF@SOP8 [DX1044]
MB95R212KPH [DX0001]
MB95R213HPF@SOP8 [DX1044]
MB95R213HPH [DX0001]
MB95R213KPF@SOP8 [DX1044]
MB95R213KPH [DX0001]
MB95R214HPF@SOP8 [DX1044]
MB95R214HPH [DX0001]

MB95R214KPF@SOP8 [DX1044]	MB95R214KPH [DX0001]
MB95R222HPF@SOP16 [DX1032]	MB95R222HPH [DX0001]
MB95R222KPF@SOP16 [DX1032]	MB95R222KPH [DX0001]
MB95R223HPF@SOP16 [DX1032]	MB95R223HPH [DX0001]
MB95R223KPF@SOP16 [DX1032]	MB95R223KPH [DX0001]
MB95R224HPF@SOP16 [DX1032]	MB95R224HPH [DX0001]
MB95R224KPF@SOP16 [DX1032]	MB95R224KPH [DX0001]
MB96F007AAPMC@QFP64 [DX3064]	MB96F007AAPMC1@QFP64 [DX3011]
MB96F007RAPMC@QFP64 [DX3064]	MB96F007RAPMC1@QFP64 [DX3011]
MB96F013AAPMC [DX3043]	MB96F013RAPMC [DX3043]
MB96F017ABPMC [DX3016]	MB96F017RBPMC [DX3016]
MB96F312AAPMC [DX3007]	MB96F312ABPMC [DX3007]
MB96F312RAPMC [DX3007]	MB96F312RBPMC [DX3007]
MB96F313AAPMC [DX3007]	MB96F313ABPMC [DX3007]
MB96F313RAPMC [DX3007]	MB96F313RBPMC [DX3007]
MB96F315AAPMC [DX3007]	MB96F315ABPMC [DX3007]
MB96F315RAPMC [DX3007]	MB96F315RBPMC [DX3007]
MB96F326RSBPMC [DX3060]	MB96F326RWBPMC [DX3060]
MB96F326YSBPMC [DX3060]	MB96F326YWBPMC [DX3060]
MB96F346ASAPMC@LQFP100 [DX3043]	MB96F346ASAPQC@QFP100 [DX3022]
MB96F346ASBPMC@LQFP100 [DX3043]	MB96F346ASBPQC@QFP100 [DX3022]
MB96F346AWAPMC@LQFP100 [DX3043]	MB96F346AWAPQC@QFP100 [DX3022]
MB96F346AWBPMC@LQFP100 [DX3043]	MB96F346AWBPQC@QFP100 [DX3022]
MB96F346RSAPMC@LQFP100 [DX3043]	MB96F346RSAPQC@QFP100 [DX3022]
MB96F346RSBPMC@LQFP100 [DX3043]	MB96F346RSBPQC@QFP100 [DX3022]
MB96F346RWAPMC@LQFP100 [DX3043]	MB96F346RWAPQC@QFP100 [DX3022]
MB96F346RWBPMC@LQFP100 [DX3043]	MB96F346RWBPQC@QFP100 [DX3022]
MB96F346YSAPMC@LQFP100 [DX3043]	MB96F346YSAPQC@QFP100 [DX3022]
MB96F346YSBPMC@LQFP100 [DX3043]	MB96F346YSBPQC@QFP100 [DX3022]
MB96F346YWAPMC@LQFP100 [DX3043]	MB96F346YWAPQC@QFP100 [DX3022]
MB96F346YWBPMC@LQFP100 [DX3043]	MB96F346YWBPQC@QFP100 [DX3022]
MB96F347ASAPMC@LQFP100 [DX3043]	MB96F347ASAPQC@QFP100 [DX3022]
MB96F347ASBPMC@LQFP100 [DX3043]	MB96F347ASBPQC@QFP100 [DX3022]
MB96F347AWAPMC@LQFP100 [DX3043]	MB96F347AWAPQC@QFP100 [DX3022]
MB96F347AWBPMC@LQFP100 [DX3043]	MB96F347AWBPQC@QFP100 [DX3022]
MB96F347RSAPMC@LQFP100 [DX3043]	MB96F347RSAPQC@QFP100 [DX3022]
MB96F347RSBPMC@LQFP100 [DX3043]	MB96F347RSBPQC@QFP100 [DX3022]
MB96F347RWAPMC@LQFP100 [DX3043]	MB96F347RWAPQC@QFP100 [DX3022]
MB96F347RWBPMC@LQFP100 [DX3043]	MB96F347RWBPQC@QFP100 [DX3022]
MB96F347YSAPMC@LQFP100 [DX3043]	MB96F347YSAPQC@QFP100 [DX3022]
MB96F347YSBPMC@LQFP100 [DX3043]	MB96F347YSBPQC@QFP100 [DX3022]
MB96F347YWAPMC@LQFP100 [DX3043]	MB96F347YWAPQC@QFP100 [DX3022]
MB96F347YWBPMC@LQFP100 [DX3043]	MB96F347YWBPQC@QFP100 [DX3022]
MB96F348ASAPMC@LQFP100 [DX3043]	MB96F348ASAPQC@QFP100 [DX3022]
MB96F348ASBPMC@LQFP100 [DX3043]	MB96F348ASBPQC@QFP100 [DX3022]
MB96F348AWAPMC@LQFP100 [DX3043]	MB96F348AWAPQC@QFP100 [DX3022]
MB96F348AWBPMC@LQFP100 [DX3043]	MB96F348AWBPQC@QFP100 [DX3022]
MB96F348HSAPMC@LQFP100 [DX3043]	MB96F348HSAPQC@QFP100 [DX3022]

MB96F348HSBPMC@LQFP100 [DX3043]	MB96F348HSBPQC@QFP100 [DX3022]
MB96F348HWAPMC@LQFP100 [DX3043]	MB96F348HWAPQC@QFP100 [DX3022]
MB96F348HWBPMC@LQFP100 [DX3043]	MB96F348HWBPQC@QFP100 [DX3022]
MB96F348RSAPMC@LQFP100 [DX3043]	MB96F348RSAPQC@QFP100 [DX3022]
MB96F348RSBPMC@LQFP100 [DX3043]	MB96F348RSBPQC@QFP100 [DX3022]
MB96F348RWAPMC@LQFP100 [DX3043]	MB96F348RWAPQC@QFP100 [DX3022]
MB96F348RWBPMC@LQFP100 [DX3043]	MB96F348RWBPQC@QFP100 [DX3022]
MB96F348TSAPMC@LQFP100 [DX3043]	MB96F348TSAPQC@QFP100 [DX3022]
MB96F348TSBPMC@LQFP100 [DX3043]	MB96F348TSBPQC@QFP100 [DX3022]
MB96F348TWAPMC@LQFP100 [DX3043]	MB96F348TWAPQC@QFP100 [DX3022]
MB96F348TWBPMC@LQFP100 [DX3043]	MB96F348TWBPQC@QFP100 [DX3022]
MB96F348YSAPMC@LQFP100 [DX3043]	MB96F348YSAPQC@QFP100 [DX3022]
MB96F348YSBPMC@LQFP100 [DX3043]	MB96F348YSBPQC@QFP100 [DX3022]
MB96F348YWAPMC@LQFP100 [DX3043]	MB96F348YWAPQC@QFP100 [DX3022]
MB96F348YWBPMC@LQFP100 [DX3043]	MB96F348YWBPQC@QFP100 [DX3022]
MB96F353ASAPMC@LQFP64 [DX3012]	MB96F353ASAPMC1@LQFP64 [DX3057]
MB96F353ASBPMC@LQFP64 [DX3012]	MB96F353ASBPMC1@LQFP64 [DX3057]
MB96F353AWAPMC@LQFP64 [DX3012]	MB96F353AWAPMC1@LQFP64 [DX3057]
MB96F353AWBPMC@LQFP64 [DX3012]	MB96F353AWBPMC1@LQFP64 [DX3057]
MB96F353RSAPMC@LQFP64 [DX3012]	MB96F353RSAPMC1@LQFP64 [DX3057]
MB96F353RSBPMC@LQFP64 [DX3012]	MB96F353RSBPMC1@LQFP64 [DX3057]
MB96F353RWAPMC@LQFP64 [DX3012]	MB96F353RWAPMC1@LQFP64 [DX3057]
MB96F353RWBPMC@LQFP64 [DX3012]	MB96F353RWBPMC1@LQFP64 [DX3057]
MB96F353YSAPMC@LQFP64 [DX3012]	MB96F353YSAPMC1@LQFP64 [DX3057]
MB96F353YSBPMC@LQFP64 [DX3012]	MB96F353YSBPMC1@LQFP64 [DX3057]
MB96F353YWAPMC@LQFP64 [DX3012]	MB96F353YWAPMC1@LQFP64 [DX3057]
MB96F353YWBPMC@LQFP64 [DX3012]	MB96F353YWBPMC1@LQFP64 [DX3057]
MB96F355ASAPMC@LQFP64 [DX3012]	MB96F355ASAPMC1@LQFP64 [DX3057]
MB96F355ASBPMC@LQFP64 [DX3012]	MB96F355ASBPMC1@LQFP64 [DX3057]
MB96F355AWAPMC@LQFP64 [DX3012]	MB96F355AWAPMC1@LQFP64 [DX3057]
MB96F355AWBPMC@LQFP64 [DX3012]	MB96F355AWBPMC1@LQFP64 [DX3057]
MB96F355RSAPMC@LQFP64 [DX3012]	MB96F355RSAPMC1@LQFP64 [DX3057]
MB96F355RSBPMC@LQFP64 [DX3012]	MB96F355RSBPMC1@LQFP64 [DX3057]
MB96F355RWAPMC@LQFP64 [DX3012]	MB96F355RWAPMC1@LQFP64 [DX3057]
MB96F355RWBPMC@LQFP64 [DX3012]	MB96F355RWBPMC1@LQFP64 [DX3057]
MB96F355YSAPMC@LQFP64 [DX3012]	MB96F355YSAPMC1@LQFP64 [DX3057]
MB96F355YSBPMC@LQFP64 [DX3012]	MB96F355YSBPMC1@LQFP64 [DX3057]
MB96F355YWAPMC@LQFP64 [DX3012]	MB96F355YWAPMC1@LQFP64 [DX3057]
MB96F355YWBPMC@LQFP64 [DX3012]	MB96F355YWBPMC1@LQFP64 [DX3057]
MB96F356ASAPMC@LQFP64 [DX3012]	MB96F356ASAPMC1@LQFP64 [DX3057]
MB96F356ASBPMC@LQFP64 [DX3012]	MB96F356ASBPMC1@LQFP64 [DX3057]
MB96F356AWAPMC@LQFP64 [DX3012]	MB96F356AWAPMC1@LQFP64 [DX3057]
MB96F356AWBPMC@LQFP64 [DX3012]	MB96F356AWBPMC1@LQFP64 [DX3057]
MB96F356RSAPMC@LQFP64 [DX3012]	MB96F356RSAPMC1@LQFP64 [DX3057]
MB96F356RSBPMC@LQFP64 [DX3012]	MB96F356RSBPMC1@LQFP64 [DX3057]
MB96F356RWAPMC@LQFP64 [DX3012]	MB96F356RWAPMC1@LQFP64 [DX3057]
MB96F356RWBPMC@LQFP64 [DX3012]	MB96F356RWBPMC1@LQFP64 [DX3057]
MB96F356YSAPMC@LQFP64 [DX3012]	MB96F356YSAPMC1@LQFP64 [DX3057]

MB96F356YSBPMC@LQFP64 [DX3012]
MB96F356YWAPMC@LQFP64 [DX3012]
MB96F356YWBPMC@LQFP64 [DX3012]
MB96F378HSBPMC [DX3035]
MB96F378HWBPMC [DX3035]
MB96F378TSBPMC [DX3035]
MB96F378TWBPMC [DX3035]
MB96F379HSBPMC [DX3035]
MB96F379HWBPMC [DX3035]
MB96F379TSBPMC [DX3035]
MB96F379TWBPMC [DX3035]
MB96F385RSAPMC@LQFP120 [DX3028]
MB96F385RSCPMC@LQFP120 [DX3028]
MB96F385RWBPMC@LQFP120 [DX3028]
MB96F385YSAPMC@LQFP120 [DX3028]
MB96F385YSCPMC@LQFP120 [DX3028]
MB96F385YWBPMC@LQFP120 [DX3028]
MB96F386RSAPMC@LQFP120 [DX3028]
MB96F386RSCPMC@LQFP120 [DX3028]
MB96F386RWBPMC@LQFP120 [DX3028]
MB96F386YSAPMC@LQFP120 [DX3028]
MB96F386YSCPMC@LQFP120 [DX3028]
MB96F386YWBPMC@LQFP120 [DX3028]
MB96F387RSAPMC@LQFP120 [DX3028]
MB96F387RSCPMC@LQFP120 [DX3028]
MB96F387RWBPMC@LQFP120 [DX3028]
MB96F387YSAPMC@LQFP120 [DX3028]
MB96F387YSCPMC@LQFP120 [DX3028]
MB96F387YWBPMC@LQFP120 [DX3028]
MB96F388HSAPMC@LQFP120 [DX3028]
MB96F388HWAPMC@LQFP120 [DX3028]
MB96F388TSAPMC@LQFP120 [DX3028]
MB96F388TWAPMC@LQFP120 [DX3028]
MB96F389RSAPMC@LQFP120 [DX3028]
MB96F389RWAPMC@LQFP120 [DX3028]
MB96F389YSAPMC@LQFP120 [DX3028]
MB96F389YWAPMC@LQFP120 [DX3028]
MB96F395RSBPMC@LQFP100 [DX3043]
MB96F612AAPMC@LQFP48 [DX3007]
MB96F612RAPMC@LQFP48 [DX3007]
MB96F613AAPMC@LQFP48 [DX3007]
MB96F613RAPMC@LQFP48 [DX3007]
MB96F615AAPMC@LQFP48 [DX3007]
MB96F615RAPMC@LQFP48 [DX3007]
MB96F622AAPMC [DX3064]
MB96F622ABPMC [DX3064]
MB96F622RAPMC [DX3064]
MB96F622RBPMC [DX3064]
MB96F356YSBPMC1@LQFP64 [DX3057]
MB96F356YWAPMC1@LQFP64 [DX3057]
MB96F356YWBPMC1@LQFP64 [DX3057]
MB96F378HSBPMC1 [DX3041]
MB96F378HWBPMC1 [DX3041]
MB96F378TSBPMC1 [DX3041]
MB96F378TWBPMC1 [DX3041]
MB96F379HSBPMC1 [DX3041]
MB96F379HWBPMC1 [DX3041]
MB96F379TSBPMC1 [DX3041]
MB96F379TWBPMC1 [DX3041]
MB96F385RSBPMC@LQFP120 [DX3028]
MB96F385RWAPMC@LQFP120 [DX3028]
MB96F385RWCPMC@LQFP120 [DX3028]
MB96F385YSBPMC@LQFP120 [DX3028]
MB96F385YWAPMC@LQFP120 [DX3028]
MB96F385YWCPMC@LQFP120 [DX3028]
MB96F386RSBPMC@LQFP120 [DX3028]
MB96F386RWAPMC@LQFP120 [DX3028]
MB96F386RWCPMC@LQFP120 [DX3028]
MB96F386YSBPMC@LQFP120 [DX3028]
MB96F386YWAPMC@LQFP120 [DX3028]
MB96F386YWCPMC@LQFP120 [DX3028]
MB96F387RSBPMC@LQFP120 [DX3028]
MB96F387RWAPMC@LQFP120 [DX3028]
MB96F387RWCPMC@LQFP120 [DX3028]
MB96F387YSBPMC@LQFP120 [DX3028]
MB96F387YWAPMC@LQFP120 [DX3028]
MB96F387YWCPMC@LQFP120 [DX3028]
MB96F388HSBPMC@LQFP120 [DX3028]
MB96F388HWBPMC@LQFP120 [DX3028]
MB96F388TSBPMC@LQFP120 [DX3028]
MB96F388TWBPMC@LQFP120 [DX3028]
MB96F389RSBPMC@LQFP120 [DX3028]
MB96F389RWBPMC@LQFP120 [DX3028]
MB96F389YSBPMC@LQFP120 [DX3028]
MB96F389YWBPMC@LQFP120 [DX3028]
MB96F395RWBPMC@LQFP100 [DX3043]
MB96F612ABPMC@LQFP48 [DX3007]
MB96F612RBPMC@LQFP48 [DX3007]
MB96F613ABPMC@LQFP48 [DX3007]
MB96F613RBPMC@LQFP48 [DX3007]
MB96F615ABPMC@LQFP48 [DX3007]
MB96F615RBPMC@LQFP48 [DX3007]
MB96F622AAPMC1 [DX3011]
MB96F622ABPMC1 [DX3011]
MB96F622RAPMC1 [DX3011]
MB96F622RBPMC1 [DX3011]

MB96F623AAPMC [DX3064]	MB96F623AAPMC1 [DX3011]
MB96F623ABPMC [DX3064]	MB96F623ABPMC1 [DX3011]
MB96F623RAPMC [DX3064]	MB96F623RAPMC1 [DX3011]
MB96F623RBPMC [DX3064]	MB96F623RBPMC1 [DX3011]
MB96F625AAPMC [DX3064]	MB96F625AAPMC1 [DX3011]
MB96F625ABPMC [DX3064]	MB96F625ABPMC1 [DX3011]
MB96F625RAPMC [DX3064]	MB96F625RAPMC1 [DX3011]
MB96F625RBPMC [DX3064]	MB96F625RBPMC1 [DX3011]
MB96F633AAPMC [DX3016]	MB96F633ABPMC [DX3016]
MB96F633RAPMC [DX3016]	MB96F633RBPMC [DX3016]
MB96F635AAPMC [DX3016]	MB96F635ABPMC [DX3016]
MB96F635RAPMC [DX3016]	MB96F635RBPMC [DX3016]
MB96F636AAPMC [DX3016]	MB96F636ABPMC [DX3016]
MB96F636RAPMC [DX3016]	MB96F636RBPMC [DX3016]
MB96F637AAPMC [DX3016]	MB96F637ABPMC [DX3016]
MB96F637RAPMC [DX3016]	MB96F637RBPMC [DX3016]
MB96F643AAPMC [DX3043]	MB96F643ABPMC [DX3043]
MB96F643RAPMC [DX3043]	MB96F643RBPMC [DX3043]
MB96F645AAPMC [DX3043]	MB96F645ABPMC [DX3043]
MB96F645RAPMC [DX3043]	MB96F645RBPMC [DX3043]
MB96F646AAPMC [DX3043]	MB96F646ABPMC [DX3043]
MB96F646RAPMC [DX3043]	MB96F646RBPMC [DX3043]
MB96F647AAPMC [DX3043]	MB96F647ABPMC [DX3043]
MB96F647RAPMC [DX3043]	MB96F647RBPMC [DX3043]
MB96F653AAPMC [DX3027]	MB96F653ABPMC [DX3027]
MB96F653RAPMC [DX3027]	MB96F653RBPMC [DX3027]
MB96F655AAPMC [DX3027]	MB96F655ABPMC [DX3027]
MB96F655RAPMC [DX3027]	MB96F655RBPMC [DX3027]
MB96F656AAPMC [DX3027]	MB96F656ABPMC [DX3027]
MB96F656RAPMC [DX3027]	MB96F656RBPMC [DX3027]
MB96F657AAPMC [DX3027]	MB96F657ABPMC [DX3027]
MB96F657RAPMC [DX3027]	MB96F657RBPMC [DX3027]
MB96F673AAPMC [DX3064]	MB96F673AAPMC1 [DX3011]
MB96F673ABPMC [DX3064]	MB96F673ABPMC1 [DX3011]
MB96F673RAPMC [DX3064]	MB96F673RAPMC1 [DX3011]
MB96F673RBPMC [DX3064]	MB96F673RBPMC1 [DX3011]
MB96F675AAPMC [DX3064]	MB96F675AAPMC1 [DX3011]
MB96F675ABPMC [DX3064]	MB96F675ABPMC1 [DX3011]
MB96F675RAPMC [DX3064]	MB96F675RAPMC1 [DX3011]
MB96F675RBPMC [DX3064]	MB96F675RBPMC1 [DX3011]
MB96F683AAPMC [DX3016]	MB96F683ABPMC [DX3016]
MB96F683RAPMC [DX3016]	MB96F683RBPMC [DX3016]
MB96F685AAPMC [DX3016]	MB96F685ABPMC [DX3016]
MB96F685RAPMC [DX3016]	MB96F685RBPMC [DX3016]
MB96F693AAPMC [DX3043]	MB96F693ABPMC [DX3043]
MB96F693RAPMC [DX3043]	MB96F693RBPMC [DX3043]
MB96F695AAPMC [DX3043]	MB96F695ABPMC [DX3043]
MB96F695RAPMC [DX3043]	MB96F695RBPMC [DX3043]

MB96F696AAPMC [DX3043]
MB96F696ABPMC [DX3043]
MB96F696RAPMC [DX3043]
MB96F696RBPMC [DX3043]
MB96F6A3AAPMC [DX3028]
MB96F6A3ABPMC [DX3028]
MB96F6A3RAPMC [DX3028]
MB96F6A3RBPMC [DX3028]
MB96F6A5AAPMC [DX3028]
MB96F6A5ABPMC [DX3028]
MB96F6A5RAPMC [DX3028]
MB96F6A5RBPMC [DX3028]
MB96F6A6AAPMC [DX3028]
MB96F6A6ABPMC [DX3028]
MB96F6A6RAPMC [DX3028]
MB96F6A6RBPMC [DX3028]
MB96F6B3AAPMC [DX3043]
MB96F6B3ABPMC [DX3043]
MB96F6B3RAPMC [DX3043]
MB96F6B3RBPMC [DX3043]
MB96F6B5AAPMC [DX3043]
MB96F6B5ABPMC [DX3043]
MB96F6B5RAPMC [DX3043]
MB96F6B5RBPMC [DX3043]
MB96F6B6AAPMC [DX3043]
MB96F6B6ABPMC [DX3043]
MB96F6B6RAPMC [DX3043]
MB96F6B6RBPMC [DX3043]
MB96F6C3AAPMC [DX3028]
MB96F6C3ABPMC [DX3028]
MB96F6C3RAPMC [DX3028]
MB96F6C3RBPMC [DX3028]
MB96F6C5AAPMC [DX3028]
MB96F6C5ABPMC [DX3028]
MB96F6C5RAPMC [DX3028]
MB96F6C5RBPMC [DX3028]
MB96F6C6AAPMC [DX3028]
MB96F6C6ABPMC [DX3028]
MB96F6C6RAPMC [DX3028]
MB96F6C6RBPMC [DX3028]
MB9AF007KAPMC [DX3007]
MB9AF007KAQN [DX4021]
MB9AF007KPMC [DX3007]
MB9AF007KQN [DX4021]
MB9AF007LAPMC [DX3064]
MB9AF007LAPMC1 [DX3011]
MB9AF007LAQN [DX4023]
MB9AF007LPMC [DX3064]
MB9AF007LPMC1 [DX3011]
MB9AF007LQN [DX4023]
MB9AF007MAPMC [DX3016]
MB9AF007MAPMC1 [DX3017]
MB9AF007MPMC [DX3016]
MB9AF007MPMC1 [DX3017]
MB9AF007NABGL [BBBB]
MB9AF007NAPF [DX3077]
MB9AF007NAPMC [DX3021]
MB9AF007NBGL [BBBB]
MB9AF007NPF [DX3077]
MB9AF007NPMC [DX3021]
MB9AF102N@LQFP100 [DX3043]
MB9AF102N@LQFP120 [DX3052]
MB9AF102R@LQFP100 [DX3043]
MB9AF102R@LQFP120 [DX3052]
MB9AF104N@LQFP100 [DX3043]
MB9AF104N@LQFP120 [DX3052]
MB9AF104R@LQFP100 [DX3043]
MB9AF104R@LQFP120 [DX3052]
MB9AF111KPMC [DX3007]
MB9AF111KPMC1 [DX3063]
MB9AF111KQN [DX4021]
MB9AF111LPMC [DX3064]
MB9AF111LPMC1 [DX3011]
MB9AF111MPMC [DX3016]
MB9AF111NBGL [BBBB]
MB9AF111NPF [DX3077]
MB9AF111NPMC [DX3021]
MB9AF112KPMC [DX3007]
MB9AF112KPMC1 [DX3063]
MB9AF112KQN [DX4021]
MB9AF112LPMC [DX3064]
MB9AF112LPMC1 [DX3011]
MB9AF112MPMC [DX3016]
MB9AF112NBGL [BBBB]
MB9AF112NPF [DX3077]
MB9AF112NPMC [DX3021]
MB9AF114KPMC [DX3007]
MB9AF114KPMC1 [DX3063]
MB9AF114KQN [DX4021]
MB9AF114LPMC [DX3064]
MB9AF114LPMC1 [DX3011]
MB9AF114MPMC [DX3016]
MB9AF114NBGL [BBBB]
MB9AF114NPF [DX3077]
MB9AF114NPMC [DX3021]
MB9AF115KPMC [DX3007]

MB9AF115KPMC1 [DX3063]
MB9AF115LPMC [DX3064]
MB9AF115MPMC [DX3016]
MB9AF115NPF [DX3077]
MB9AF116KPMC [DX3007]
MB9AF116KQN [DX4021]
MB9AF116LPMC1 [DX3011]
MB9AF116NBGL [BBBB]
MB9AF116NPMC [DX3021]
MB9AF131KAQN [DX4021]
MB9AF131KQN [DX4021]
MB9AF131LAPMC1 [DX3011]
MB9AF131LPMC [DX3064]
MB9AF131LQN [DX4023]
MB9AF131MAPMC1 [DX3017]
MB9AF131MPMC1 [DX3017]
MB9AF131NAPF [DX3077]
MB9AF131NBGL [BBBB]
MB9AF131NPMC [DX3021]
MB9AF132KAQN [DX4021]
MB9AF132KQN [DX4021]
MB9AF132LAPMC1 [DX3011]
MB9AF132LPMC [DX3064]
MB9AF132LQN [DX4023]
MB9AF132MAPMC1 [DX3017]
MB9AF132MPMC1 [DX3017]
MB9AF132NAPF [DX3077]
MB9AF132NBGL [BBBB]
MB9AF132NPMC [DX3021]
MB9AF134KAQN [DX4021]
MB9AF134KQN [DX4021]
MB9AF134LAPMC1 [DX3011]
MB9AF134LPMC [DX3064]
MB9AF134LQN [DX4023]
MB9AF134MAPMC1 [DX3017]
MB9AF134MPMC1 [DX3017]
MB9AF134NAPF [DX3077]
MB9AF134NBGL [BBBB]
MB9AF134NPMC [DX3021]
MB9AF135KAQN [DX4021]
MB9AF135KQN [DX4021]
MB9AF135LAPMC1 [DX3011]
MB9AF135LPMC [DX3064]
MB9AF135LQN [DX4023]
MB9AF135MAPMC1 [DX3017]
MB9AF135MPMC1 [DX3017]
MB9AF135NAPF [DX3077]
MB9AF135NBGL [BBBB]
MB9AF115KQN [DX4021]
MB9AF115LPMC1 [DX3011]
MB9AF115NBGL [BBBB]
MB9AF115NPMC [DX3021]
MB9AF116KPMC1 [DX3063]
MB9AF116LPMC [DX3064]
MB9AF116MPMC [DX3016]
MB9AF116NPF [DX3077]
MB9AF131KAPMC [DX3007]
MB9AF131KPMC [DX3007]
MB9AF131LAPMC [DX3064]
MB9AF131LAQN [DX4023]
MB9AF131LPMC1 [DX3011]
MB9AF131MAPMC [DX3016]
MB9AF131MPMC [DX3016]
MB9AF131NABGL [BBBB]
MB9AF131NAPMC [DX3021]
MB9AF131NPF [DX3077]
MB9AF132KAPMC [DX3007]
MB9AF132KPMC [DX3007]
MB9AF132LAPMC [DX3064]
MB9AF132LAQN [DX4023]
MB9AF132LPMC1 [DX3011]
MB9AF132MAPMC [DX3016]
MB9AF132MPMC [DX3016]
MB9AF132NABGL [BBBB]
MB9AF132NAPMC [DX3021]
MB9AF132NPF [DX3077]
MB9AF134KAPMC [DX3007]
MB9AF134KPMC [DX3007]
MB9AF134LAPMC [DX3064]
MB9AF134LAQN [DX4023]
MB9AF134LPMC1 [DX3011]
MB9AF134MAPMC [DX3016]
MB9AF134MPMC [DX3016]
MB9AF134NABGL [BBBB]
MB9AF134NAPMC [DX3021]
MB9AF134NPF [DX3077]
MB9AF135KAPMC [DX3007]
MB9AF135KPMC [DX3007]
MB9AF135LAPMC [DX3064]
MB9AF135LAQN [DX4023]
MB9AF135LPMC1 [DX3011]
MB9AF135MAPMC [DX3016]
MB9AF135MPMC [DX3016]
MB9AF135NABGL [BBBB]
MB9AF135NAPMC [DX3021]
MB9AF135NPF [DX3077]

MB9AF135NPMC [DX3021]
MB9AF136KAQN [DX4021]
MB9AF136KQN [DX4021]
MB9AF136LAPMC1 [DX3011]
MB9AF136LPMC [DX3064]
MB9AF136LQN [DX4023]
MB9AF136MAPMC1 [DX3017]
MB9AF136MPMC1 [DX3017]
MB9AF136NAPF [DX3077]
MB9AF136NBGL [BBBB]
MB9AF136NPMC [DX3021]
MB9AF141KQN [DX4021]
MB9AF141LPMC1 [DX3011]
MB9AF141MBGL [DX0001]
MB9AF141MPMC1 [DX3018]
MB9AF141NPF [DX3077]
MB9AF142KPMC [DX3007]
MB9AF142LPMC [DX3064]
MB9AF142LQN [DX4023]
MB9AF142MPMC [DX3016]
MB9AF142NBGL [BBBB]
MB9AF142NPMC [DX3021]
MB9AF144KQN [DX4021]
MB9AF144LPMC1 [DX3011]
MB9AF144MBGL [DX0001]
MB9AF144MPMC1 [DX3018]
MB9AF144NPF [DX3077]
MB9AF145KPMC [DX3007]
MB9AF145LPMC [DX3064]
MB9AF145LQN [DX4023]
MB9AF145MPMC [DX3016]
MB9AF145NBGL [BBBB]
MB9AF145NPMC [DX3021]
MB9AF146KQN [DX4021]
MB9AF146LPMC1 [DX3011]
MB9AF146MBGL [DX0001]
MB9AF146MPMC1 [DX3018]
MB9AF146NPF [DX3077]
MB9AF311KPMC [DX3007]
MB9AF311KQN [DX4021]
MB9AF311LPMC1 [DX3011]
MB9AF311NBGL [BBBB]
MB9AF311NPMC [DX3021]
MB9AF312KPMC1 [DX3063]
MB9AF312LPMC [DX3064]
MB9AF312MPMC [DX3016]
MB9AF312NPF [DX3077]
MB9AF314KPMC [DX3007]
MB9AF136KAPMC [DX3007]
MB9AF136KPMC [DX3007]
MB9AF136LAPMC [DX3064]
MB9AF136LAQN [DX4023]
MB9AF136LPMC1 [DX3011]
MB9AF136MAPMC [DX3016]
MB9AF136MPMC [DX3016]
MB9AF136NABGL [BBBB]
MB9AF136NAPMC [DX3021]
MB9AF136NPF [DX3077]
MB9AF141KPMC [DX3007]
MB9AF141LPMC [DX3064]
MB9AF141LQN [DX4023]
MB9AF141MPMC [DX3016]
MB9AF141NBGL [BBBB]
MB9AF141NPMC [DX3021]
MB9AF142KQN [DX4021]
MB9AF142LPMC1 [DX3011]
MB9AF142MBGL [DX0001]
MB9AF142MPMC1 [DX3018]
MB9AF142NPF [DX3077]
MB9AF144KPMC [DX3007]
MB9AF144LPMC [DX3064]
MB9AF144LQN [DX4023]
MB9AF144MPMC [DX3016]
MB9AF144NBGL [BBBB]
MB9AF144NPMC [DX3021]
MB9AF145KQN [DX4021]
MB9AF145LPMC1 [DX3011]
MB9AF145MBGL [DX0001]
MB9AF145MPMC1 [DX3018]
MB9AF145NPF [DX3077]
MB9AF146KPMC [DX3007]
MB9AF146LPMC [DX3064]
MB9AF146LQN [DX4023]
MB9AF146MPMC [DX3016]
MB9AF146NBGL [BBBB]
MB9AF146NPMC [DX3021]
MB9AF311KPMC1 [DX3063]
MB9AF311LPMC [DX3064]
MB9AF311MPMC [DX3016]
MB9AF311NPF [DX3077]
MB9AF312KPMC [DX3007]
MB9AF312KQN [DX4021]
MB9AF312LPMC1 [DX3011]
MB9AF312NBGL [BBBB]
MB9AF312NPMC [DX3021]
MB9AF314KPMC1 [DX3063]

MB9AF314KQN [DX4021]
MB9AF314LPMC [DX3064]
MB9AF314LPMC1 [DX3011]
MB9AF314MPMC [DX3016]
MB9AF314NBGL [BBBB]
MB9AF314NPF [DX3077]
MB9AF314NPMC [DX3021]
MB9AF315KPMC [DX3007]
MB9AF315KPMC1 [DX3063]
MB9AF315KQN [DX4021]
MB9AF315LPMC [DX3064]
MB9AF315LPMC1 [DX3011]
MB9AF315MPMC [DX3016]
MB9AF315NBGL [BBBB]
MB9AF315NPF [DX3077]
MB9AF315NPMC [DX3021]
MB9AF316KPMC [DX3007]
MB9AF316KPMC1 [DX3063]
MB9AF316KQN [DX4021]
MB9AF316LPMC [DX3064]
MB9AF316LPMC1 [DX3011]
MB9AF316MPMC [DX3016]
MB9AF316NBGL [BBBB]
MB9AF316NPF [DX3077]
MB9AF316NPMC [DX3021]
MB9AF341KPMC [DX3007]
MB9AF341KQN [DX4021]
MB9AF341LPMC [DX3064]
MB9AF341LPMC1 [DX3011]
MB9AF341LQN [DX4023]
MB9AF341MBGL [DX0001]
MB9AF341MPMC [DX3016]
MB9AF341MPMC1 [DX3018]
MB9AF341NBGL [BBBB]
MB9AF341NPF [DX3077]
MB9AF341NPMC [DX3021]
MB9AF342KPMC [DX3007]
MB9AF342KQN [DX4021]
MB9AF342LPMC [DX3064]
MB9AF342LPMC1 [DX3011]
MB9AF342LQN [DX4023]
MB9AF342MBGL [DX0001]
MB9AF342MPMC [DX3016]
MB9AF342MPMC1 [DX3018]
MB9AF342NBGL [BBBB]
MB9AF342NPF [DX3077]
MB9AF342NPMC [DX3021]
MB9AF344KPMC [DX3007]
MB9AF344KQN [DX4021]
MB9AF344LPMC [DX3064]
MB9AF344LPMC1 [DX3011]
MB9AF344LQN [DX4023]
MB9AF344MBGL [DX0001]
MB9AF344MPMC [DX3016]
MB9AF344MPMC1 [DX3018]
MB9AF344NBGL [BBBB]
MB9AF344NPF [DX3077]
MB9AF344NPMC [DX3021]
MB9AF345KPMC [DX3007]
MB9AF345KQN [DX4021]
MB9AF345LPMC [DX3064]
MB9AF345LPMC1 [DX3011]
MB9AF345LQN [DX4023]
MB9AF345MBGL [DX0001]
MB9AF345MPMC [DX3016]
MB9AF345MPMC1 [DX3018]
MB9AF345NBGL [BBBB]
MB9AF345NPF [DX3077]
MB9AF345NPMC [DX3021]
MB9AF346KPMC [DX3007]
MB9AF346KQN [DX4021]
MB9AF346LPMC [DX3064]
MB9AF346LPMC1 [DX3011]
MB9AF346LQN [DX4023]
MB9AF346MBGL [DX0001]
MB9AF346MPMC [DX3016]
MB9AF346MPMC1 [DX3018]
MB9AF346NBGL [BBBB]
MB9AF346NPF [DX3077]
MB9AF346NPMC [DX3021]
MB9AFA31KAPMC [DX3007]
MB9AFA31KAQN [DX4021]
MB9AFA31KPMC [DX3007]
MB9AFA31KQN [DX4021]
MB9AFA31LAPMC [DX3064]
MB9AFA31LAPMC1 [DX3011]
MB9AFA31LAQN [DX4023]
MB9AFA31LPMC [DX3064]
MB9AFA31LPMC1 [DX3011]
MB9AFA31LQN [DX4023]
MB9AFA31MAPMC [DX3016]
MB9AFA31MAPMC1 [DX3017]
MB9AFA31MPMC [DX3016]
MB9AFA31MPMC1 [DX3017]
MB9AFA31NABGL [BBBB]
MB9AFA31NAPF [DX3077]

MB9AFA31NAPMC [DX3021]
MB9AFA31NBGL [BBBB]
MB9AFA31NPF [DX3077]
MB9AFA31NPMC [DX3021]
MB9AFA32KAPMC [DX3007]
MB9AFA32KAQN [DX4021]
MB9AFA32KPMC [DX3007]
MB9AFA32KQN [DX4021]
MB9AFA32LAPMC [DX3064]
MB9AFA32LAPMC1 [DX3011]
MB9AFA32LAQN [DX4023]
MB9AFA32LPMC [DX3064]
MB9AFA32LPMC1 [DX3011]
MB9AFA32LQN [DX4023]
MB9AFA32MAPMC [DX3016]
MB9AFA32MAPMC1 [DX3017]
MB9AFA32MPMC [DX3016]
MB9AFA32MPMC1 [DX3017]
MB9AFA32NABGL [BBBB]
MB9AFA32NAPF [DX3077]
MB9AFA32NAPMC [DX3021]
MB9AFA32NBGL [BBBB]
MB9AFA32NPF [DX3077]
MB9AFA32NPMC [DX3021]
MB9AFA34KAPMC [DX3007]
MB9AFA34KAQN [DX4021]
MB9AFA34KPMC [DX3007]
MB9AFA34KQN [DX4021]
MB9AFA34LAPMC [DX3064]
MB9AFA34LAPMC1 [DX3011]
MB9AFA34LAQN [DX4023]
MB9AFA34LPMC [DX3064]
MB9AFA34LPMC1 [DX3011]
MB9AFA34LQN [DX4023]
MB9AFA34MAPMC [DX3016]
MB9AFA34MAPMC1 [DX3017]
MB9AFA34MPMC [DX3016]
MB9AFA34MPMC1 [DX3017]
MB9AFA34NABGL [BBBB]
MB9AFA34NAPF [DX3077]
MB9AFA34NAPMC [DX3021]
MB9AFA34NBGL [BBBB]
MB9AFA34NPF [DX3077]
MB9AFA34NPMC [DX3021]
MB9AFA35KAPMC [DX3007]
MB9AFA35KAQN [DX4021]
MB9AFA35KPMC [DX3007]
MB9AFA35KQN [DX4021]
MB9AFA35LAPMC [DX3064]
MB9AFA35LAPMC1 [DX3011]
MB9AFA35LAQN [DX4023]
MB9AFA35LPMC [DX3064]
MB9AFA35LPMC1 [DX3011]
MB9AFA35LQN [DX4023]
MB9AFA35MAPMC [DX3016]
MB9AFA35MAPMC1 [DX3017]
MB9AFA35MPMC [DX3016]
MB9AFA35MPMC1 [DX3017]
MB9AFA35NABGL [BBBB]
MB9AFA35NAPF [DX3077]
MB9AFA35NAPMC [DX3021]
MB9AFA35NBGL [BBBB]
MB9AFA35NPF [DX3077]
MB9AFA35NPMC [DX3021]
MB9AFA36KAPMC [DX3007]
MB9AFA36KAQN [DX4021]
MB9AFA36KPMC [DX3007]
MB9AFA36KQN [DX4021]
MB9AFA36LAPMC [DX3064]
MB9AFA36LAPMC1 [DX3011]
MB9AFA36LAQN [DX4023]
MB9AFA36LPMC [DX3064]
MB9AFA36LPMC1 [DX3011]
MB9AFA36LQN [DX4023]
MB9AFA36MAPMC [DX3016]
MB9AFA36MAPMC1 [DX3017]
MB9AFA36MPMC [DX3016]
MB9AFA36MPMC1 [DX3017]
MB9AFA36NABGL [BBBB]
MB9AFA36NAPF [DX3077]
MB9AFA36NAPMC [DX3021]
MB9AFA36NBGL [BBBB]
MB9AFA36NPF [DX3077]
MB9AFA36NPMC [DX3021]
MB9AFA41KPMC [DX3007]
MB9AFA41KQN [DX4021]
MB9AFA41LPMC [DX3064]
MB9AFA41LPMC1 [DX3011]
MB9AFA41LQN [DX4023]
MB9AFA41MBGL [DX0001]
MB9AFA41MPMC [DX3016]
MB9AFA41MPMC1 [DX3018]
MB9AFA41NBGL [BBBB]
MB9AFA41NPF [DX3077]
MB9AFA41NPMC [DX3021]
MB9AFA42KPMC [DX3007]

MB9AFA42KQN [DX4021]
MB9AFA42LPMC [DX3064]
MB9AFA42LPMC1 [DX3011]
MB9AFA42LQN [DX4023]
MB9AFA42MBGL [DX0001]
MB9AFA42MPMC [DX3016]
MB9AFA42MPMC1 [DX3018]
MB9AFA42NBGL [BBBB]
MB9AFA42NPF [DX3077]
MB9AFA42NPMC [DX3021]
MB9AFA44KPMC [DX3007]
MB9AFA44KQN [DX4021]
MB9AFA44LPMC [DX3064]
MB9AFA44LPMC1 [DX3011]
MB9AFA44LQN [DX4023]
MB9AFA44MBGL [DX0001]
MB9AFA44MPMC [DX3016]
MB9AFA44MPMC1 [DX3018]
MB9AFA44NBGL [BBBB]
MB9AFA44NPF [DX3077]
MB9AFA44NPMC [DX3021]
MB9AFA45KPMC [DX3007]
MB9AFA45KQN [DX4021]
MB9AFA45LPMC [DX3064]
MB9AFA45LPMC1 [DX3011]
MB9AFA45LQN [DX4023]
MB9AFA45MBGL [DX0001]
MB9AFA45MPMC [DX3016]
MB9AFA45MPMC1 [DX3018]
MB9AFA45NBGL [BBBB]
MB9AFA45NPF [DX3077]
MB9AFA45NPMC [DX3021]
MB9AFA46KPMC [DX3007]
MB9AFA46KQN [DX4021]
MB9AFA46LPMC [DX3064]
MB9AFA46LPMC1 [DX3011]
MB9AFA46LQN [DX4023]
MB9AFA46MBGL [DX0001]
MB9AFA46MPMC [DX3016]
MB9AFA46MPMC1 [DX3018]
MB9AFA46NBGL [BBBB]
MB9AFA46NPF [DX3077]
MB9AFA46NPMC [DX3021]
MB9AFB41KPMC [DX3007]
MB9AFB41KQN [DX4021]
MB9AFB41LPMC [DX3064]
MB9AFB41LPMC1 [DX3011]
MB9AFB41LQN [DX4023]
MB9AFB41MBGL [DX0001]
MB9AFB41MPMC [DX3016]
MB9AFB41MPMC1 [DX3018]
MB9AFB41NBGL [BBBB]
MB9AFB41NPF [DX3077]
MB9AFB41NPMC [DX3021]
MB9AFB42KPMC [DX3007]
MB9AFB42KQN [DX4021]
MB9AFB42LPMC [DX3064]
MB9AFB42LPMC1 [DX3011]
MB9AFB42LQN [DX4023]
MB9AFB42MBGL [DX0001]
MB9AFB42MPMC [DX3016]
MB9AFB42MPMC1 [DX3018]
MB9AFB42NBGL [BBBB]
MB9AFB42NPF [DX3077]
MB9AFB42NPMC [DX3021]
MB9AFB44KPMC [DX3007]
MB9AFB44KQN [DX4021]
MB9AFB44LPMC [DX3064]
MB9AFB44LPMC1 [DX3011]
MB9AFB44LQN [DX4023]
MB9AFB44MBGL [DX0001]
MB9AFB44MPMC [DX3016]
MB9AFB44MPMC1 [DX3018]
MB9AFB44NBGL [BBBB]
MB9AFB44NPF [DX3077]
MB9AFB44NPMC [DX3021]
MB9AFB45KPMC [DX3007]
MB9AFB45KQN [DX4021]
MB9AFB45LPMC [DX3064]
MB9AFB45LPMC1 [DX3011]
MB9AFB45LQN [DX4023]
MB9AFB45MBGL [DX0001]
MB9AFB45MPMC [DX3016]
MB9AFB45MPMC1 [DX3018]
MB9AFB45NBGL [BBBB]
MB9AFB45NPF [DX3077]
MB9AFB45NPMC [DX3021]
MB9AFB46KPMC [DX3007]
MB9AFB46KQN [DX4021]
MB9AFB46LPMC [DX3064]
MB9AFB46LPMC1 [DX3011]
MB9AFB46LQN [DX4023]
MB9AFB46MBGL [DX0001]
MB9AFB46MPMC [DX3016]
MB9AFB46MPMC1 [DX3018]
MB9AFB46NBGL [BBBB]

MB9AFB46NPF [DX3077]
MB9AFB46NPMC [DX3021]
MB9BF104N@BGA112P [DX0001]
MB9BF104N@LQFP100 [DX3043]
MB9BF104N@LQFP120 [DX3052]
MB9BF104R@BGA112P [DX0001]
MB9BF104R@LQFP100 [DX3043]
MB9BF104R@LQFP120 [DX3052]
MB9BF105N@BGA112P [DX0001]
MB9BF105N@LQFP100 [DX3043]
MB9BF105N@LQFP120 [DX3052]
MB9BF105R@BGA112P [DX0001]
MB9BF105R@LQFP100 [DX3043]
MB9BF105R@LQFP120 [DX3052]
MB9BF106N@BGA112P [DX0001]
MB9BF106N@LQFP100 [DX3043]
MB9BF106N@LQFP120 [DX3052]
MB9BF106R@BGA112P [DX0001]
MB9BF106R@LQFP100 [DX3043]
MB9BF106R@LQFP120 [DX3052]
MB9BF112N@LQFP100 [DX3043]
MB9BF112N@LQFP120 [DX3052]
MB9BF112R@LQFP100 [DX3043]
MB9BF112R@LQFP120 [DX3052]
MB9BF114N@LQFP100 [DX3043]
MB9BF114N@LQFP120 [DX3052]
MB9BF114R@LQFP100 [DX3043]
MB9BF114R@LQFP120 [DX3052]
MB9BF115N@LQFP100 [DX3043]
MB9BF115N@LQFP120 [DX3052]
MB9BF115R@LQFP100 [DX3043]
MB9BF115R@LQFP120 [DX3052]
MB9BF116N@LQFP100 [DX3043]
MB9BF116N@LQFP120 [DX3052]
MB9BF116R@LQFP100 [DX3043]
MB9BF116R@LQFP120 [DX3052]
MB9BF121KPMC [DX3007]
MB9BF121KQN [DX4021]
MB9BF121LPMC [DX3064]
MB9BF121LPMC1 [DX3011]
MB9BF121LQN [DX4023]
MB9BF121MBGL [DX0001]
MB9BF121MPMC [DX3016]
MB9BF121MPMC1 [DX3018]
MB9BF122KPMC [DX3007]
MB9BF122KQN [DX4021]
MB9BF122LPMC [DX3064]
MB9BF122LPMC1 [DX3011]
MB9BF122LQN [DX4023]
MB9BF122MBGL [DX0001]
MB9BF122MPMC [DX3016]
MB9BF122MPMC1 [DX3018]
MB9BF124KPMC [DX3007]
MB9BF124KQN [DX4021]
MB9BF124LPMC [DX3064]
MB9BF124LPMC1 [DX3011]
MB9BF124LQN [DX4023]
MB9BF124MBGL [DX0001]
MB9BF124MPMC [DX3016]
MB9BF124MPMC1 [DX3018]
MB9BF125KPMC [DX3007]
MB9BF125KQN [DX4021]
MB9BF125LPMC [DX3064]
MB9BF125LPMC1 [DX3011]
MB9BF125LQN [DX4023]
MB9BF125MBGL [DX0001]
MB9BF125MPMC [DX3016]
MB9BF125MPMC1 [DX3018]
MB9BF126KPMC [DX3007]
MB9BF126KQN [DX4021]
MB9BF126LPMC [DX3064]
MB9BF126LPMC1 [DX3011]
MB9BF126LQN [DX4023]
MB9BF126MBGL [DX0001]
MB9BF126MPMC [DX3016]
MB9BF126MPMC1 [DX3018]
MB9BF304N@BGA112P [DX0001]
MB9BF304N@LQFP100 [DX3043]
MB9BF304N@LQFP120 [DX3052]
MB9BF304R@BGA112P [DX0001]
MB9BF304R@LQFP100 [DX3043]
MB9BF304R@LQFP120 [DX3052]
MB9BF305N@BGA112P [DX0001]
MB9BF305N@LQFP100 [DX3043]
MB9BF305N@LQFP120 [DX3052]
MB9BF305R@BGA112P [DX0001]
MB9BF305R@LQFP100 [DX3043]
MB9BF305R@LQFP120 [DX3052]
MB9BF306N@BGA112P [DX0001]
MB9BF306N@LQFP100 [DX3043]
MB9BF306N@LQFP120 [DX3052]
MB9BF306R@BGA112P [DX0001]
MB9BF306R@LQFP100 [DX3043]
MB9BF306R@LQFP120 [DX3052]
MB9BF312N@LQFP100 [DX3043]
MB9BF312N@LQFP120 [DX3052]

MB9BF312R@LQFP100 [DX3043]
MB9BF312R@LQFP120 [DX3052]
MB9BF314N@LQFP100 [DX3043]
MB9BF314N@LQFP120 [DX3052]
MB9BF314R@LQFP100 [DX3043]
MB9BF314R@LQFP120 [DX3052]
MB9BF315N@LQFP100 [DX3043]
MB9BF315N@LQFP120 [DX3052]
MB9BF315R@LQFP100 [DX3043]
MB9BF315R@LQFP120 [DX3052]
MB9BF316N@LQFP100 [DX3043]
MB9BF316N@LQFP120 [DX3052]
MB9BF316R@LQFP100 [DX3043]
MB9BF316R@LQFP120 [DX3052]
MB9BF321KPMC [DX3007]
MB9BF321KQN [DX4021]
MB9BF321LPMC [DX3064]
MB9BF321LPMC1 [DX3011]
MB9BF321LQN [DX4023]
MB9BF321MBGL [DX0001]
MB9BF321MPMC [DX3016]
MB9BF321MPMC1 [DX3018]
MB9BF322KPMC [DX3007]
MB9BF322KQN [DX4021]
MB9BF322LPMC [DX3064]
MB9BF322LPMC1 [DX3011]
MB9BF322LQN [DX4023]
MB9BF322MBGL [DX0001]
MB9BF322MPMC [DX3016]
MB9BF322MPMC1 [DX3018]
MB9BF324KPMC [DX3007]
MB9BF324KQN [DX4021]
MB9BF324LPMC [DX3064]
MB9BF324LPMC1 [DX3011]
MB9BF324LQN [DX4023]
MB9BF324MBGL [DX0001]
MB9BF324MPMC [DX3016]
MB9BF324MPMC1 [DX3018]
MB9BF325KPMC [DX3007]
MB9BF325KQN [DX4021]
MB9BF325LPMC [DX3064]
MB9BF325LPMC1 [DX3011]
MB9BF325LQN [DX4023]
MB9BF325MBGL [DX0001]
MB9BF325MPMC [DX3016]
MB9BF325MPMC1 [DX3018]
MB9BF326KPMC [DX3007]
MB9BF326KQN [DX4021]
MB9BF326LPMC [DX3064]
MB9BF326LPMC1 [DX3011]
MB9BF326LQN [DX4023]
MB9BF326MBGL [DX0001]
MB9BF326MPMC [DX3016]
MB9BF326MPMC1 [DX3018]
MB9BF404N@BGA112P [DX0001]
MB9BF404N@LQFP100 [DX3043]
MB9BF404N@LQFP120 [DX3052]
MB9BF404R@BGA112P [DX0001]
MB9BF404R@LQFP100 [DX3043]
MB9BF404R@LQFP120 [DX3052]
MB9BF405N@BGA112P [DX0001]
MB9BF405N@LQFP100 [DX3043]
MB9BF405N@LQFP120 [DX3052]
MB9BF405R@BGA112P [DX0001]
MB9BF405R@LQFP100 [DX3043]
MB9BF405R@LQFP120 [DX3052]
MB9BF406N@BGA112P [DX0001]
MB9BF406N@LQFP100 [DX3043]
MB9BF406N@LQFP120 [DX3052]
MB9BF406R@BGA112P [DX0001]
MB9BF406R@LQFP100 [DX3043]
MB9BF406R@LQFP120 [DX3052]
MB9BF412N@LQFP100 [DX3043]
MB9BF412N@LQFP120 [DX3052]
MB9BF412R@LQFP100 [DX3043]
MB9BF412R@LQFP120 [DX3052]
MB9BF414N@LQFP100 [DX3043]
MB9BF414N@LQFP120 [DX3052]
MB9BF414R@LQFP100 [DX3043]
MB9BF414R@LQFP120 [DX3052]
MB9BF415N@LQFP100 [DX3043]
MB9BF415N@LQFP120 [DX3052]
MB9BF415R@LQFP100 [DX3043]
MB9BF415R@LQFP120 [DX3052]
MB9BF416N@LQFP100 [DX3043]
MB9BF416N@LQFP120 [DX3052]
MB9BF416R@LQFP100 [DX3043]
MB9BF416R@LQFP120 [DX3052]
MB9BF504N@BGA112P [DX0001]
MB9BF504N@LQFP100 [DX3043]
MB9BF504N@LQFP120 [DX3052]
MB9BF504R@BGA112P [DX0001]
MB9BF504R@LQFP100 [DX3043]
MB9BF504R@LQFP120 [DX3052]
MB9BF505N@BGA112P [DX0001]
MB9BF505N@LQFP100 [DX3043]

MB9BF505N@LQFP120 [DX3052]
MB9BF505R@LQFP100 [DX3043]
MB9BF506N@BGA112P [DX0001]
MB9BF506N@LQFP120 [DX3052]
MB9BF506R@LQFP100 [DX3043]
MB9BF512N@LQFP100 [DX3043]
MB9BF512R@LQFP100 [DX3043]
MB9BF514N@LQFP100 [DX3043]
MB9BF514R@LQFP100 [DX3043]
MB9BF515N@LQFP100 [DX3043]
MB9BF515R@LQFP100 [DX3043]
MB9BF516N@LQFP100 [DX3043]
MB9BF516R@LQFP100 [DX3043]
MB9BF521KPMC [DX3007]
MB9BF521LPMC [DX3064]
MB9BF521LQN [DX4023]
MB9BF521MPMC [DX3016]
MB9BF522KPMC [DX3007]
MB9BF522LPMC [DX3064]
MB9BF522LQN [DX4023]
MB9BF522MPMC [DX3016]
MB9BF524KPMC [DX3007]
MB9BF524LPMC [DX3064]
MB9BF524LQN [DX4023]
MB9BF524MPMC [DX3016]
MB9BF525KPMC [DX3007]
MB9BF525LPMC [DX3064]
MB9BF525LQN [DX4023]
MB9BF525MPMC [DX3016]
MB9BF526KPMC [DX3007]
MB9BF526LPMC [DX3064]
MB9BF526LQN [DX4023]
MB9BF526MPMC [DX3016]
MBG041 [DX5216]
MBG043(old) [DX0001]
MBG048(old) [DX0001]
MBL8742N [DX0001]
MBL8749N [DX0001]
MB9BF505R@BGA112P [DX0001]
MB9BF505R@LQFP120 [DX3052]
MB9BF506N@LQFP100 [DX3043]
MB9BF506R@BGA112P [DX0001]
MB9BF506R@LQFP120 [DX3052]
MB9BF512N@LQFP120 [DX3052]
MB9BF512R@LQFP120 [DX3052]
MB9BF514N@LQFP120 [DX3052]
MB9BF514R@LQFP120 [DX3052]
MB9BF515N@LQFP120 [DX3052]
MB9BF515R@LQFP120 [DX3052]
MB9BF516N@LQFP120 [DX3052]
MB9BF516R@LQFP120 [DX3052]
MB9BF521KQN [DX4021]
MB9BF521LPMC1 [DX3011]
MB9BF521MBGL [DX0001]
MB9BF521MPMC1 [DX3018]
MB9BF522KQN [DX4021]
MB9BF522LPMC1 [DX3011]
MB9BF522MBGL [DX0001]
MB9BF522MPMC1 [DX3018]
MB9BF524KQN [DX4021]
MB9BF524LPMC1 [DX3011]
MB9BF524MBGL [DX0001]
MB9BF524MPMC1 [DX3018]
MB9BF525KQN [DX4021]
MB9BF525LPMC1 [DX3011]
MB9BF525MBGL [DX0001]
MB9BF525MPMC1 [DX3018]
MB9BF526KQN [DX4021]
MB9BF526LPMC1 [DX3011]
MB9BF526MBGL [DX0001]
MB9BF526MPMC1 [DX3018]
MBG043 [DX5214]
MBG048 [DX5214]
MBL8742H [DX0001]
MBL8749H [DX0001]

FULLRICH

E(E)PROM/FRAM/NVRAM

S29GL032N90TFI03 [DX1004]
W25Q16CVSSIG [DX1044#1]
W25Q16DWSSIG [DX1044#1]
W25Q32BVZPIH [DX4005#1]
S29GL064N90TFI02 [DX1011]
W25Q16DVSSIG [DX1044#1]
W25Q32BVSSIG [DX1044#1]
W25Q32DWZEIG [DX4006#1]

W25Q32DWZPIG [DX4005#1]
W25Q32FVSSIG [DX1044#1]
W25Q64CVSSIG [DX1044#1]
W25Q64FVZPIG [DX4005#1]
W25Q80BVSSIG [DX1044#1]
W25Q80BVZPIG [DX4005#1]
W25Q80DWSSIG [DX1044#1]

MICROCONTROLLER

CY8C20434@QFN32 [DX4015]
CY8C20437@MLF32 [DX4015]
CY8C20437S@MLF32 [DX4015]
CY8C20447@MLF32 [DX4015]
CY8C20447S@MLF32 [DX4015]
CY8C20467@MLF32 [DX4015]
CY8C20467S@MLF32 [DX4015]
CY8C20497@MLF32 [DX4015]
CY8C20497S@MLF32 [DX4015]
CY8C20637@QFN48 [DX4043]
CY8C20647@QFN48 [DX4043]
CY8C20667@QFN48 [DX4043]
CY8C21434@QFN32 [DX4015]
CY8C21434B@QFN32 [DX4015]
CY8C21634@QFN32 [DX4015]
CY8C21634B@QFN32 [DX4015]
CY8CTMA140 [DX0001]
CY8CTMA140@QFN36 [DX4042]
CY8CTMA140@QFN48 [DX4043]
CY8CTMA140E [DX0001]
CY8CTMA140E@QFN36 [DX4042]
CY8CTMA140E@QFN48 [DX4043]
CY8CTMA300E@QFN36 [DX4042]
CY8CTMA300E@QFN48 [DX4043]
CY8CTMA340@QFN36 [DX4042]
CY8CTMA340@QFN48 [DX4043]
CY8CTMA375@QFN36 [DX4042]
CY8CTMA375@QFN48 [DX4043]
CY8CTMA375E@QFN36 [DX4042]
CY8CTMA375E@QFN48 [DX4043]
CY8CTMG200@QFN32 [DX4015]
CY8CTMG200A@QFN32 [DX4015]
CY8CTMG201@QFN32 [DX4015]
CY8CTMG201A@QFN32 [DX4015]
CY8CTMG240@QFN32 [DX4015]
CY8CTMG240A@QFN32 [DX4015]
CY8CTST200@QFN24 [DX4012]
CY8CTST200@QFN32 [DX4015]
CY8CTST200A@QFN24 [DX4012]
CY8CTST200A@QFN32 [DX4015]
CY8CTST201@QFN32 [DX4015]
CY8CTST201A@QFN32 [DX4015]
CY8CTST241@QFN32 [DX4015]
CY8CTST241A@QFN32 [DX4015]
CY8CTST242 [DX0001]
CY8CTST242@QFN32 [DX4015]
CY8CTST242A [DX0001]
CY8CTST242A@QFN32 [DX4015]
EM78P468NBL@QFP64 [BBBB]
EM78P468NBQ@QFP44 [DX3003]
EM78P468NBQ@QFP64 [DX3015]
EM78P468NBQ@QFP64A [DX3044]
EM78P468NBQL@QFP44 [DX3046]
EPF025R [DX3085-1]
FR01A@QFP64 [DX3085-1]
FR02A@QFP64 [DX3085-2]
FR03A [DX3057-11]
FR03C [DX1025-1]
FR03D [DX3127]
FR05A@QFP64 [DX3085-1]
FRC7KK [DX5229-1]
MX25L1633EM2I [DX1044#1]
MX25L1633EZNI [DX4005#1]
MX25L8035EM2I [DX1044]
N25Q128A13ESE40E [DX1044#1]
S29AL008J70BFI02 [DX5043]
S29JL032H70TFI31 [DX1004]
SST25VF016B-V8 [DX1044#1]
SST25VF080B-V8 [DX1044#1]

GAMMA

E(E)PROM/FRAM/NVRAM

GAMNXX001JF9TC@TSOP48 [DX1004-3]

GATELEVEL

E(E)PROM/FRAM/NVRAM

GM24LC02B [DX0001]
GM24LC02B@SOIC8 [DX1045]
GM24LC02B@TSSOP8 [DX1059]
GM24LC04B [DX0001]
GM24LC04B@SOIC8 [DX1045]
GM24LC04B@TSSOP8 [DX1059]
GM24LC08B [DX0001]
GM24LC08B@SOIC8 [DX1045]
GM24LC08B@TSSOP8 [DX1059]
GM24LC16B [DX0001]
GM24LC16B@SOIC8 [DX1045]
GM24LC16B@TSSOP8 [DX1059]

GENCORE

MICROCONTROLLER

GC87C520A0 [DX0001]
GC87C520A0@PLCC44 [DX2044]
GC87C520A0@TQFP44 [DX3003]
GC87C520G0 [DX0001]
GC87C520G0@PLCC44 [DX2044]
GC87C520G0@TQFP44 [DX3003]
GC89L541A0@LQFP44 [DX3002]
GC89L541A0@MLF32 [DX4015]
GC89L541A0@MQFP44 [DX3066]
GC89L541A0@PQFP44 [DX3066]
GC89L541A0@QFN32 [DX4015]
GC89L581A0@LQFP44 [DX3002]
GC89L581A0@MLF32 [DX4015]
GC89L581A0@MQFP44 [DX3066]
GC89L581A0@PQFP44 [DX3066]
GC89L581A0@QFN32 [DX4015]
GC89L591A0@LQFP44 [DX3002]
GC89L591A0@MLF32 [DX4015]
GC89L591A0@MQFP44 [DX3066]
GC89L591A0@PQFP44 [DX3066]
GC89L591A0@QFN32 [DX4015]

GENERAL(GI)

E(E)PROM/FRAM/NVRAM

27256 [DX0001]
27C128 [DX0001]
27C128@PLCC32 [DX2032]
27C256 [DX0001]
27C256@PLCC32 [DX2032]
27C512 [DX0001]
27C513 [DX0001]
27C64 [DX0001]
27C64@PLCC32 [DX2032]
27HC191 [DX0001]
27HC291 [DX0001]
27HC64 [DX0001]
27HC641 [DX0001]
27HC641L [DX0001]
27HC64L [DX0001]
28C04 [DX0001]
28C04A [DX0001]
28C04F [DX0001]
28C16 [DX0001]
28C16A [DX0001]
28C16F [DX0001]
28C17 [DX0001]
28C17F [DX0001]
ER5911 [DX0001]

ER5911@SOIC8 [DX1045]
GI5911@SOIC8 [DX1045]
GI59C11@SOIC8 [DX1045]
GI59C12@SOIC8 [DX1045]
GI5911 [DX0001]
GI59C11 [DX0001]
GI59C12 [DX0001]
GR27C513 [DX0001]

GENERALPLUS

E(E)PROM/FRAM/NVRAM

GPR25L005E@SOP8 [DX1045#1]
GPR25L011E@SOP8 [DX1045#1]
GPR25L021B@SOP8 [DX1045#1]
GPR25L041B@SOP8 [DX1045#1]
GPR25L081B@SOP8 [DX1045#1]
GPR25L1284E@SOP16 [DX1033#1]
GPR25L162B@SOP8 [DX1045#1]
GPR25L322B@SOP8 [DX1045#1]
GPR25L6404E@SOP16 [DX1033#1]
GPR25L6404E@SOP16(OTP) [DX1033#1]
GPR25L6404E@SOP8 [DX1044#1]
GPR25L6404E@SOP8(OTP) [DX1044#1]

MICROCONTROLLER

GPM8F2002A@SOP8 [DX1045]
GPM8F2202A@SOP16 [DX1016]
GPM8F3108A@QFP44 [DX3003]
GPM8F3116A@QFP44 [DX3003]
GPM8F3132A@QFP44 [DX3003]

GENERIC

E(E)PROM/FRAM/NVRAM

27128(21V)
27128A(12.5V) [DX0001]
2716(25V) [DX0001]
27256(12.5V) [DX0001]
2732(25V) [DX0001]
2732A(21V) [DX0001]
2732B(12.5V) [DX0001]
27512(12.5V) [DX0001]
27512(21V) [DX0001]
2764(21V) [DX0001]
2764A(12.5V) [DX0001]
27C128(12.5V) [DX0001]
27C128(21V) [DX0001]
27C16(25V) [DX0001]
27C256(12.5V) [DX0001]
27C32(25V) [DX0001]
27C512(12.5V) [DX0001]
27C64(12.5V) [DX0001]
27C64(21V) [DX0001]

GENITOP

E(E)PROM/FRAM/NVRAM

GT16G80 [DX0001]
GT16G80@SOP16 [DX1033#1]
GT16G80@SOP8 [DX1044#1]
GT16G80@VDFN8 [DX4006#1]
GT25Q16A@SOP8[150 mil] [DX1045#1]

GT25Q16A@SOP8[200 mil] [DX1044#1]
GT25Q16A@USON8 [DX1045#1]
GT25Q32A@SOP8[150 mil] [DX1045#1]
GT25Q32A@SOP8[200 mil] [DX1044#1]
GT25Q80A@SOP8[150 mil] [DX1045#1]
GT25Q80A@SOP8[200 mil] [DX1044#1]
GT25Q80A@USON8 [DX1045#1]
GT32G16 [DX0001]
GT32G16@SOP16 [DX1033#1]
GT32G16@SOP8 [DX1044#1]
GT32G16@VDFN8 [DX4006#1]
GT32G40 [DX0001#1]
GT32G40@SOP16 [DX1033#1]
GT32G40@SOP8 [DX1044#1]
GT32G40@VDFN8 [DX4005#1]
GT40G10 [DX0001]
GT40G10@SOP16 [DX1033#1]
GT40G10@SOP8 [DX1044#1]
GT40G10@VDFN8 [DX4006#1]
GT64G80 [DX0001]
GT64G80@SOP8 [DX1044#1]
GT64G80@VDFN8-1 [DX4005#1]
GT64G80@VDFN8-2 [DX4006#1]

GENUSION

E(E)PROM/FRAM/NVRAM

G28FVW5121S1TE@TSOP56 [DX1055]

GIANTEC

E(E)PROM/FRAM/NVRAM

GT24C01 [DX0001]
GT24C01@MSOP8 [DX1015]
GT24C01@SOP8 [DX1045]
GT24C01@TSOT23 [DX1041]
GT24C01@TSSOP8 [DX1059]
GT24C02 [DX0001]
GT24C02@DFN8 [DX4047]
GT24C02@MSOP8 [DX1015]
GT24C02@SOP8 [DX1045]
GT24C02@TSOT23 [DX1041]
GT24C02@TSSOP8 [DX1059]
GT24C04 [DX0001]
GT24C04@DFN8 [DX1015]
GT24C04@MSOP8 [DX1015]
GT24C04@SOP8 [DX1045]
GT24C04@TSOT23 [DX1041]
GT24C04@TSSOP8 [DX1059]
GT24C08 [DX0001]
GT24C08@DFN8 [DX4047]
GT24C08@MSOP8 [DX1015]
GT24C08@SOP8 [DX1045]
GT24C08@TSOT23 [DX1041]
GT24C08@TSSOP8 [DX1059]
GT24C128 [DX0001]
GT24C128@SOP8 [DX1045]
GT24C128@TSSOP14 [DX1000]
GT24C16 [DX0001]
GT24C16@DFN8 [DX1015]
GT24C16@MSOP8 [DX1015]
GT24C16@SOP8 [DX1045]
GT24C16@TSSOP8 [DX1059]
GT24C256 [DX0001]
GT24C256@SOP8 [DX1045]
GT24C256@TSSOP14 [DX1000]
GT24C32 [DX0001]
GT24C32@MSOP8 [DX1015]
GT24C32@SOP8 [DX1045]
GT24C32@TSSOP8 [DX1059]
GT24C32@UDFN8 [DX4047]
GT24C64 [DX0001]

GT24C64@MSOP8 [DX1015]
GT24C64@SOP8 [DX1045]
GT24C64@TSSOP8 [DX1059]
GT24C64@UDFN8 [DX4047]
GT24C64A [DX0001]
GT24C64A@MSOP8 [DX1015]
GT24C64A@SOP8 [DX1045]
GT24C64A@TSSOP8 [DX1059]
GT24C64A@UDFN8 [DX4047]
GT24E64@SOP8 [DX1045]
GT24E64@TSSOP8 [DX1059]
GT25C01 [DX0001]
GT25C01@SOP8 [DX1045]
GT25C01@TSSOP8 [DX1059]
GT25C02 [DX0001]
GT25C02@SOP8 [DX1045]
GT25C02@TSSOP8 [DX1059]
GT25C04 [DX0001]
GT25C04@SOP8 [DX1045]
GT25C04@TSSOP8
GT25C08 [DX0001]
GT25C08@SOIC8 [DX1045]
GT25C08@TSSOP8 [DX1059]
GT25C128@SOIC8 [DX1045]
GT25C128@TSSOP8 [DX1059]
GT25C16 [DX0001]
GT25C16@SOIC8 [DX1045]
GT25C16@TSSOP8 [DX1059]
GT25C256@SOIC8 [DX1045]
GT25C256@TSSOP8 [DX1059]
GT25C32 [DX0001]
GT25C32@SOIC8 [DX1045]
GT25C32@TSSOP8 [DX1059]
GT25C64 [DX0001]
GT25C64@SOIC8 [DX1045]
GT25C64@TSSOP8 [DX1059]
GT34C02 [DX0001]
GT34C02@MSOP8 [DX1015]
GT34C02@SOP8 [DX1045]
GT34C02@TSSOP8 [DX1059]
GT93C46(08bit) [DX0001]
GT93C46(08bit)@SOIC8 [DX1045]
GT93C46(08bit)@TSSOP8 [DX1059]
GT93C46(16bit) [DX0001]
GT93C46(16bit)@SOIC8 [DX1045]
GT93C46(16bit)@TSSOP8 [DX1059]
GT93C56(08bit) [DX0001]
GT93C56(08bit)@SOIC8 [DX1045]
GT93C56(08bit)@TSSOP8 [DX1059]
GT93C56(16bit) [DX0001]
GT93C56(16bit)@SOIC8 [DX1045]
GT93C56(16bit)@TSSOP8 [DX1059]
GT93C66(08bit) [DX0001]
GT93C66(08bit)@SOIC8 [DX1045]
GT93C66(08bit)@TSSOP8 [DX1059]
GT93C66(16bit) [DX0001]
GT93C66(16bit)@SOIC8 [DX1045]
GT93C66(16bit)@TSSOP8 [DX1059]
GT93C76(08bit) [DX0001]
GT93C76(08bit)@SOIC8 [DX1045]
GT93C76(08bit)@TSSOP8 [DX1059]
GT93C76(16bit) [DX0001]
GT93C76(16bit)@SOIC8 [DX1045]
GT93C76(16bit)@TSSOP8 [DX1059]
GT93C86(08bit) [DX0001]
GT93C86(08bit)@SOIC8 [DX1045]
GT93C86(08bit)@TSSOP8 [DX1059]
GT93C86(16bit) [DX0001]
GT93C86(16bit)@SOIC8 [DX1045]
GT93C86(16bit)@TSSOP8 [DX1059]

MICROCONTROLLER

GT34TS04-2GLI [DX1045]
GT34TS04-2UDLI [DX4002]

GIGADEVICE

E(E)PROM/FRAM/NVRAM

GD25B128C [DX0001#1]
GD25B128C@SOIC16 [DX1033#1]
GD25B128C@SOIC8 [DX1044#1]
GD25B128C@SON8 [DX4005#1]

GD25B128C@TFBGA24[5*5] [DX5157]
GD25B128C@TFBGA24[6*4] [DX5146]
GD25B128C@VSOP8 [DX1044#1]
GD25B128C@WSON8 [DX4006#1]
GD25B16B [DX0001]
GD25B16B@SOP16 [DX1072#1]
GD25B16B@SOP8[150mil] [DX1045#1]
GD25B16B@SOP8[200mil] [DX1044#1]
GD25B16B@TFBGA24 [DX5146]
GD25B16B@WSON8 [DX4005#1]
GD25B32B [DX0001]
GD25B32B@SOP16 [DX1072#1]
GD25B32B@SOP8 [DX1044#1]
GD25B32B@TFBGA24 [DX5146]
GD25B32B@WSON8 [DX4005#1]
GD25B64B [DX0001]
GD25B64B@SOP16 [DX1072#1]
GD25B64B@SOP8 [DX1044#1]
GD25B64B@TFBGA24 [DX5146]
GD25B64B@WSON8 [DX4005#1]
GD25D05B@SOP8 [DX1045#1]
GD25D05B@TSSOP8 [DX1059#3]
GD25D05B@USON8 [DX4076#1]
GD25D10B@SOP8 [DX1045#1]
GD25D10B@TSSOP8 [DX1059#3]
GD25D10B@USON8 [DX4076#1]
GD25D40 [DX0001]
GD25D40@SOP8 [DX1044#1]
GD25D80 [DX0001]
GD25D80@SOP8 [DX1044#1]
GD25E16 [DX0001]
GD25E16@SOP8 [DX1044#1]
GD25E40 [DX0001]
GD25E40@SOP8 [DX1044#1]
GD25E40@TSSOP8 [DX1045#1]
GD25E64B@SOP8 [DX1044#1]
GD25E80B [DX0001]
GD25E80B@SOP8 [DX1044#1]
GD25E80B@TSSOP8 [DX1045#1]
GD25F40 [DX0001]
GD25F40@SOP8 [DX1044#1]
GD25F80 [DX0001]
GD25F80@SOP8 [DX1044#1]
GD25LQ128@SOP16 [DX1072#1]
GD25LQ128@SOP8 [DX1044#1]
GD25LQ128@WSON8 [DX4006#1]
GD25LQ16@SOP8 [DX1044#1]
GD25LQ16@TSOP8 [DX1044#1]
GD25LQ16@USON8 [DX4081#1]
GD25LQ16@WSON8 [DX4005#1]
GD25LQ20B@SOP8 [DX1045#1]
GD25LQ20B@TSOP8 [DX1059#3]
GD25LQ20B@USON8 [DX4005#1]
GD25LQ20B@WSON8 [DX4005#1]
GD25LQ32@SOP8 [DX1044#1]
GD25LQ32@WSON8 [DX4005#1]
GD25LQ40@SOP8 [DX1045#1]
GD25LQ40@TSOP8 [DX1059#3]
GD25LQ40@USON8 [DX4005#1]
GD25LQ40@WSON8 [DX4005#1]
GD25LQ40B@SOP8 [DX1045#1]
GD25LQ40B@TSOP8 [DX1059#3]
GD25LQ40B@USON8 [DX4005#1]
GD25LQ40B@WSON8 [DX4005#1]
GD25LQ512C@WSON8 [DX4006#1]
GD25LQ64@TSOP8 [DX1044#1]
GD25LQ64@WSON8 [DX4005#1]
GD25LQ64B@SOP16 [DX1072#1]
GD25LQ64B@SOP8 [DX1044#1]
GD25LQ64B@WSON8 [DX4005#1]
GD25LQ64C@SOP16 [DX1072#1]
GD25LQ64C@SOP8 [DX1044#1]
GD25LQ64C@WSON8 [DX4005#1]
GD25LQ80@SOP8 [DX1045#1]
GD25LQ80@USON8 [DX4081#1]
GD25LQ80@WSON8 [DX4005#1]
GD25LQ80B@SOP8 [DX1045#1]
GD25LQ80B@USON8 [DX4081#1]
GD25LQ80B@WSON8 [DX4005#1]
GD25M21B@SOIC8 [DX1045#1]
GD25M21B@TSSOP8 [DX1059#3]
GD25M21B@USON8 [DX4002#1]
GD25M41B@SOIC8 [DX1045#1]
GD25M41B@TSSOP8 [DX1059#3]
GD25M41B@USON8 [DX4002#1]
GD25Q10 [DX0001]
GD25Q10@SOP8(150 mil) [DX1045#1]
GD25Q10@SOP8(200 mil) [DX1044#1]
GD25Q10@USON8 [DX4002#1]
GD25Q128B@SOP16 [DX1072#1]
GD25Q128B@WSON8 [DX4006#1]
GD25Q128C [DX0001]
GD25Q128C@SOP16 [DX1072#1]
GD25Q128C@SOP8 [DX1044#1]
GD25Q128C@TFBGA24 [DX5146]
GD25Q128C@TSOP8 [DX1044#1]

GD25Q128C@WSON8 [DX4006#1]
GD25Q16 [DX0001]
GD25Q16@SOP8 [DX1044#1]
GD25Q16B [DX0001]
GD25Q16B@SOP8 [DX1044#1]
GD25Q16C [DX0001]
GD25Q16C@SOP8 [DX1044#1]
GD25Q20 [DX0001]
GD25Q20@SOP8(150 mil) [DX1045#1]
GD25Q20@SOP8(200 mil) [DX1044#1]
GD25Q20@USON8 [DX4047#1]
GD25Q20B@SOIC8 [DX1045#1]
GD25Q20B@TSSOP8 [DX1059#3]
GD25Q20B@USON8 [DX4047#1]
GD25Q21B@SOIC8 [DX1045#1]
GD25Q21B@TSSOP8 [DX1059#3]
GD25Q21B@USON8 [DX4047#1]
GD25Q256C@SOIC16 [DX1033#1]
GD25Q256C@TFBGA24[5*5] [DX5157]
GD25Q256C@TFBGA24[6*4] [DX5146]
GD25Q256C@WSON8 [DX4006#1]
GD25Q32 [DX0001]
GD25Q32(4*256 Security) [DX1044#1]
GD25Q32@SOP8 [DX1044#1]
GD25Q32@SOP8(4*256 Security) [DX1044#1]
GD25Q32B [DX0001]
GD25Q32B@SOP8 [DX1044#1]
GD25Q32B@TFBGA24 [DX5146]
GD25Q32C [DX0001]
GD25Q32C@SOP8 [DX1044#1]
GD25Q32C@TFBGA24 [DX5146]
GD25Q40 [DX0001]
GD25Q40@SOP8(150 mil) [DX1045#1]
GD25Q40@SOP8(200 mil) [DX1044#1]
GD25Q40@USON8 [DX4002#1]
GD25Q40B@SOIC8 [DX1045#1]
GD25Q40B@TSSOP8 [DX1059#3]
GD25Q40B@USON8 [DX4002#1]
GD25Q41B@SOIC8 [DX1045#1]
GD25Q41B@TSSOP8 [DX1059#3]
GD25Q41B@USON8 [DX4002#1]
GD25Q512 [DX0001]
GD25Q512@SOP8 [DX1045#1]
GD25Q512@TSSOP8 [DX1059#3]
GD25Q512@USON8 [DX4002#1]
GD25Q512MC@SOIC16 [DX1033#1]
GD25Q512MC@TFBGA24[5*5] [DX5157]
GD25Q512MC@TFBGA24[6*4] [DX5146]
GD25Q512MC@WSON8 [DX4006#1]
GD25Q64B [DX0001]
GD25Q64B@SOP16 [DX1072#1]
GD25Q64B@SOP8 [DX1044#1]
GD25Q64B@TFBGA24 [DX5146]
GD25Q64B@TSOP8 [DX1044#1]
GD25Q64B@WSON8[6*5] [DX4005#1]
GD25Q64B@WSON8[6*8] [DX4006#1]
GD25Q64C@SOP16 [DX1072#1]
GD25Q64C@SOP8 [DX1044#1]
GD25Q64C@TFBGA24 [DX5146]
GD25Q64C@TSOP8 [DX1044#1]
GD25Q64C@WSON8 [DX4005#1]
GD25Q80 [DX0001]
GD25Q80@SOP8(150 mil) [DX1045#1]
GD25Q80@SOP8(200 mil) [DX1044#1]
GD25Q80B [DX0001]
GD25Q80B@SOP8(150 mil) [DX1045#1]
GD25Q80B@SOP8(200 mil) [DX1044#1]
GD25Q80B@USON8 [DX4002#1]
GD25Q80C [DX0001]
GD25Q80C@SOP8(150 mil) [DX1045#1]
GD25Q80C@SOP8(200 mil) [DX1044#1]
GD25Q80C@USON8 [DX4002#1]
GD25T80 [DX0001]
GD25T80@SOP8 [DX1044#1]
GD25VQ21B@SOIC8 [DX1045#1]
GD25VQ21B@TSSOP8 [DX1059#3]
GD25VQ21B@USON8 [DX4002#1]
GD25VQ41B@SOIC8 [DX1045#1]
GD25VQ41B@TSSOP8 [DX1059#3]
GD25VQ41B@USON8 [DX4002#1]
GD29GL064CAB@FBGA48 [DX5002]
GD32F130C4@LQFP48 [DX3007]
GD32F130C6@LQFP48 [DX3007]
GD32F130C8@LQFP48 [DX3007]
GD32F130F4@TSSOP20 [DX1000]
GD32F130G4@QFN28 [DX4036]
GD32F130G6@QFN28 [DX4036]
GD32F130G8@QFN28 [DX4036]
GD32F130R8@LQFP64 [DX3011]

GD32F150C4@LQFP48 [DX3007]
GD32F150C6@LQFP48 [DX3007]
GD32F150C8@LQFP48 [DX3007]
GD32F150G4@QFN28 [DX4036]
GD32F150G6@QFN28 [DX4036]
GD32F150G8@QFN28 [DX4036]
GD32F150K4@QFN32 [DX4015]
GD32F150K6@QFN32 [DX4015]
GD32F150K8@QFN32 [DX4015]
GD32F150R4@LQFN64 [DX3011]
GD32F150R6@LQFN64 [DX3011]
GD32F150R8@LQFN64 [DX3011]
GD5F1GQ4UAYIG
GD5F1GQ4UBYIG@WSON8
MD25D16 [DX0001]
MD25D16@SOP8(150 mil) [DX1044#1]
MD25D16@SOP8(200 mil) [DX1045#1]
MD25D20 [DX0001]
MD25D20@SOP8(150 mil) [DX1045#1]
MD25D20@SOP8(200 mil) [DX1044#1]
MD25D20@USON8 [DX4002#1]
MD25D40 [DX0001]
MD25D40@SOP8(150 mil) [DX1045#1]
MD25D40@SOP8(200 mil) [DX1044#1]
MD25D40@USON8 [DX4002#1]
MD25D80 [DX0001]
MD25D80@SOP8(150 mil) [DX1045#1]
MD25D80@SOP8(200 mil) [DX1044#1]
MD5N01G51MSD1B@BGA130 [DX5140-1]
S64M80GX [DX0001#1]
S64M80GX@SOP16 [DX1033#1]
S64M80GX@SOP8 [DX1044#1]
S64M80GX@TFBGA24 [DX5146]
S64M80GX@WSON8 [DX4006#1]

MICROCONTROLLER

GD32F101C4@Q48 [DX3007]
GD32F101C6@Q48 [DX3007]
GD32F101C8@Q48 [DX3007]
GD32F101CB@Q48 [DX3007]
GD32F101R4@Q64 [DX3011]
GD32F101R6@Q64 [DX3011]
GD32F101R8@Q64 [DX3011]
GD32F101RB@Q64 [DX3011]
GD32F101RC@Q64 [DX3011]
GD32F101RD@Q64 [DX3011]
GD32F101RE@Q64 [DX3011]
GD32F101RF@Q64 [DX3011]
GD32F101RG@Q64 [DX3011]
GD32F101RI@Q64 [DX3011]
GD32F101RK@Q64 [DX3011]
GD32F101T4@N36 [DX4029]
GD32F101T6@N36 [DX4029]
GD32F101T8@N36 [DX4029]
GD32F101TB@N36 [DX4029]
GD32F101V8@Q100 [DX3043]
GD32F101VB@Q100 [DX3043]
GD32F101VC@Q100 [DX3043]
GD32F101VD@Q100 [DX3043]
GD32F101VE@Q100 [DX3043]
GD32F101VF@Q100 [DX3043]
GD32F101VG@Q100 [DX3043]
GD32F101VI@Q100 [DX3043]
GD32F101VK@Q100 [DX3043]
GD32F101ZC@Q144 [DX3035]
GD32F101ZD@Q144 [DX3035]
GD32F101ZE@Q144 [DX3035]
GD32F101ZF@Q144 [DX3035]
GD32F101ZG@Q144 [DX3035]
GD32F101ZI@Q144 [DX3035]
GD32F101ZK@Q144 [DX3035]
GD32F103C4@LQFP48 [DX3007]
GD32F103C6@LQFP48 [DX3007]
GD32F103C8@LQFP48 [DX3007]
GD32F103CB@LQFP48 [DX3007]
GD32F103R4@LQFP64 [DX3011]
GD32F103R6@LQFP64 [DX3011]
GD32F103R8@LQFP64 [DX3011]
GD32F103RB@LQFP64 [DX3011]
GD32F103RC@LQFP64 [DX3011]
GD32F103RD@LQFP64 [DX3011]
GD32F103RE@LQFP64 [DX3011]
GD32F103RF@LQFP64 [DX3011]
GD32F103RG@LQFP64 [DX3011]
GD32F103RI@LQFP64 [DX3011]
GD32F103RK@LQFP64 [DX3011]
GD32F103T4@QFN36 [DX4029]
GD32F103T6@QFN36 [DX4029]
GD32F103T8@QFN36 [DX4029]
GD32F103TB@QFN36 [DX4029]

GD32F103V8@LQFP100 [DX3043]
GD32F103VB@LQFP100 [DX3043]
GD32F103VC@LQFP100 [DX3043]
GD32F103VD@LQFP100 [DX3043]
GD32F103VE@LQFP100 [DX3043]
GD32F103VF@LQFP100 [DX3043]
GD32F103VG@LQFP100 [DX3043]
GD32F103VI@LQFP100 [DX3043]
GD32F103VK@LQFP100 [DX3043]
GD32F103ZC@Q144 [DX3035]
GD32F103ZD@Q144 [DX3035]
GD32F103ZE@Q144 [DX3035]
GD32F103ZF@Q144 [DX3035]
GD32F103ZG@Q144 [DX3035]
GD32F103ZI@Q144 [DX3035]
GD32F103ZK@Q144 [DX3035]
GD32F105R8@Q64 [DX3011]
GD32F105RB@Q64 [DX3011]
GD32F105RC@Q64 [DX3011]
GD32F105RD@Q64 [DX3011]
GD32F105RE@Q64 [DX3011]
GD32F105RF@Q64 [DX3011]
GD32F105RG@Q64 [DX3011]
GD32F105V8@Q100 [DX3043]
GD32F105VB@Q100 [DX3043]
GD32F105VC@Q100 [DX3043]
GD32F105VD@Q100 [DX3043]
GD32F105VE@Q100 [DX3043]
GD32F105VF@Q100 [DX3043]
GD32F105VG@Q100 [DX3043]
GD32F105ZC@Q144 [DX3035]
GD32F105ZD@Q144 [DX3035]
GD32F105ZE@Q144 [DX3035]
GD32F105ZF@Q144 [DX3035]
GD32F105ZG@Q144 [DX3035]
GD32F107RB@Q64 [DX3011]
GD32F107RC@Q64 [DX3011]
GD32F107RD@Q64 [DX3011]
GD32F107RE@Q64 [DX3011]
GD32F107RF@Q64 [DX3011]
GD32F107RG@Q64 [DX3011]
GD32F107VB@Q100 [DX3043]
GD32F107VC@Q100 [DX3043]
GD32F107VD@Q100 [DX3043]
GD32F107VE@Q100 [DX3043]
GD32F107VF@Q100 [DX3043]
GD32F107VG@Q100 [DX3043]
GD32F107ZC@Q144 [DX3035]
GD32F107ZD@Q144 [DX3035]
GD32F107ZE@Q144 [DX3035]
GD32F107ZF@Q144 [DX3035]
GD32F107ZG@Q144 [DX3035]

GMT

E(E)PROM/FRAM/NVRAM

AUO-G1422.29@TQFN32 [DX4015]

MICROCONTROLLER

G1601A@QFN28 [DX4013]
G1632@QFN32 [DX4015]
G1632@QFN32(Left Down) [DX4015]

GOAL

MICROCONTROLLER

VRS1000 [DX0001]
VRS1000@PLCC44 [DX2044]
VRS1000@TQFP44 [DX3003]
VRS1050 [DX0001]
VRS1050@PLCC44 [DX2044]
VRS1050@TQFP44 [DX3003]
VRS1100 [DX0001]
VRS1100@PLCC44 [DX2044]

VRS1100@TQFP44 [DX3003]
VRS540 [DX0001]
VRS540@PLCC44 [DX2044]
VRS540@TQFP44 [DX3003]
VRS550 [DX0001]
VRS550@PLCC44 [DX2044]
VRS550@TQFP44 [DX3003]
VRS560 [DX0001]
VRS560@PLCC44 [DX2044]
VRS560@TQFP44 [DX3003]
VRS570 [DX0001]
VRS570@PLCC44 [DX2044]
VRS570@TQFP44 [DX3003]
VRS580 [DX0001]
VRS580@PLCC44 [DX2044]
VRS580@TQFP44 [DX3003]
VRS700 [DX0001]
VRS700@PLCC44 [DX2044]
VRS700@TQFP44 [DX3003]
VRS900 [DX0001]
VRS900@PLCC44 [DX2044]
VRS900@TQFP44 [DX3003]

GOODIX

MICROCONTROLLER

GT9293@MLF68 [DX4026]

GOULD

PLD

PEEL153 [DX0001]
PEEL173 [DX0001]
PEEL18CV8J@PLCC20 [DX2020]
PEEL18CV8P [DX0001]
PEEL18CV8S@SOIC20 [DX1033]
PEEL18CV8T@TSOP20 [DX1000]
PEEL253 [DX0001]
PEEL273 [DX0001]

GREEN-ENGINE

E(E)PROM/FRAM/NVRAM

GE24C01 [DX0001]
GE24C01@SOP8 [DX1045]
GE24C01@TSSOP8 [DX1059]
GE24C02 [DX0001]
GE24C02@SOP8 [DX1045]
GE24C02@TSSOP8 [DX1059]
GE24C04 [DX0001]
GE24C04@SOP8 [DX1045]
GE24C04@TSSOP8 [DX1059]

GREENLIANT

E(E)PROM/FRAM/NVRAM

GLS29EE512 [DX0001]
GLS29EE512@PLCC32 [DX2032]
GLS29EE512@TSOP32 [DX1002]
GLS29EE512@VSOP32 [DX1003]
GLS29SF020@PLCC32 [DX2032]
GLS29SF020@VSOP32 [DX1003]
GLS29SF040@PLCC32 [DX2032]
GLS29SF040@VSOP32 [DX1003]

GLS29VF020@PLCC32 [DX2032]
GLS29VF020@VSOP32 [DX1003]
GLS29VF040@PLCC32 [DX2032]
GLS29VF040@VSOP32 [DX1003]
GLS37VF010 [DX0001]
GLS37VF010@PLCC32 [DX2032]
GLS37VF010@VSOP32 [DX1003]
GLS37VF020 [DX0001]
GLS37VF020@PLCC32 [DX2032]
GLS37VF020@VSOP32 [DX1003]
GLS37VF040 [DX0001]
GLS37VF040@PLCC32 [DX2032]
GLS37VF040@VSOP32 [DX1003]
GLS37VF512 [DX0001]
GLS37VF512@PLCC32 [DX2032]
GLS37VF512@VSOP32 [DX1003]
SST36VF1601G@FBGA48 [DX5002]
SST36VF1601G@FBGA56 [DX5005]
SST36VF1601G@TSOP48 [DX1004]
SST36VF1602G@FBGA48 [DX5002]
SST36VF1602G@FBGA56 [DX5005]
SST36VF1602G@TSOP48 [DX1004]
SST36VF3203@FBGA48 [DX5002]
SST36VF3203@TSOP48 [DX1004]
SST36VF3204@FBGA48 [DX5002]
SST36VF3204@TSOP48 [DX1004]

GREENWICH

E(E)PROM/FRAM/NVRAM

GR27128 [DX0001]
GR27256 [DX0001]
GR27512 [DX0001]
GR2764 [DX0001]

GSI

E(E)PROM/FRAM/NVRAM

GS8160Z36BT-200@TQFP100 [DX3062]

GTM

E(E)PROM/FRAM/NVRAM

GP24BC01 [DX0001]
GP24BC01@SOP8 [DX1045]
GP24BC01@TSSOP8 [DX1059]
GP24BC02 [DX0001]
GP24BC02@SOP8 [DX1045]
GP24BC02@TSSOP8 [DX1059]
GP24BC04 [DX0001]
GP24BC04@SOP8 [DX1045]
GP24BC04@TSSOP8 [DX1059]
GP24BC08 [DX0001]
GP24BC08@SOP8 [DX1045]
GP24BC08@TSSOP8 [DX1059]
GP24BC16 [DX0001]
GP24BC16@SOP8 [DX1045]
GP24BC16@TSSOP8 [DX1059]

HAIER

MICROCONTROLLER

HR6P58P1D1L [DX0001]
HR6P58P1D2L [DX0001]

HR6P58P1RL@SSOP10 [DX1026]
HR6P58P1S2L [DX1045]
HR6P58P1YL@SOP14 [DX1033]
HR6P59P2D2HL [DX0001]
HR6P59P2DHL [DX0001]
HR6P59P2DL [DX0001]
HR6P59P2RHL@SSOP10 [DX1026]
HR6P59P2S2HL [DX1044]
HR6P59P2SHL@SOP14 [DX1033]
HR6P59P2SL@SOP14 [DX1016]
HR6P59P2YHL [DX1045]
HR6P60P2D2HL [DX0001]
HR6P60P2DL [DX0001]
HR6P60P2DLA [DX0001]
HR6P60P2EL [DX0001]
HR6P60P2ELA [DX0001]
HR6P60P2RHL@SSOP20 [DX1000]
HR6P60P2RL@SSOP20 [DX1026]
HR6P60P2RLA@SSOP20 [DX1026]
HR6P60P2S1HL@SOP20 [DX1033]
HR6P60P2S2HL@SOP18 [DX1033]
HR6P60P2SL@SOP20 [DX1033]
HR6P60P2SLA@SOP20 [DX1033]
HR6P60P2XL@SOP18 [DX1033]
HR6P60P2XLA@SOP18 [DX1033]
HR6P60P2YL@SOP14 [DX1033]
HR6P60P2YLA@SOP14 [DX1033]
HR6P61P2D1L [DX0001]
HR6P61P2D2L [DX0001]
HR6P61P2D3L [DX0001]
HR6P61P2D4L [DX0001]
HR6P61P2S1L@SOP20 [DX1033]
HR6P61P2S2L@SOP18 [DX1033]
HR6P61P2S3L@SOP16 [DX1033]
HR6P61P2S4L@SOP14 [DX1033]
HR6P62P4D [DX0001]
HR6P62P4DH [DX0001]
HR6P62P4DHL [DX0001]
HR6P62P4DHL(INTOSC) [DX0001]
HR6P62P4DHL-D [DX0001]
HR6P62P4DHL-D(INTOSC) [DX0001]
HR6P62P4NHL(INTOSC)@SOP20 [DX1026]
HR6P62P4NHL@SSOP20 [DX1026]
HR6P62P4NHLD(INTOSC)@SSOP20 [DX1026]
HR6P62P4NHLD@SSOP20 [DX1026]
HR6P62P4RHL(INTOSC)@SOP20 [DX1026]
HR6P62P4RHL@SSOP20 [DX1026]
HR6P62P4RHL-D(INTOSC)@SSOP20 [DX1026]
HR6P62P4RHL-D@SSOP20 [DX1026]
HR6P62P4SH@SOP20 [DX1033]
HR6P62P4SHL(INTOSC)@SOP20 [DX1033]
HR6P62P4SHL@SOP20 [DX1033]
HR6P62P4SHLD(INTOSC)@SOP20 [DX1033]
HR6P62P4SHLD@SOP20 [DX1033]
HR6P62P4XHL(INTOSC)@SOP18 [DX1033]
HR6P62P4XHL@SOP18 [DX1033]
HR6P62P4XHL-D(INTOSC)@SOP18 [DX1033]
HR6P62P4XHL-D@SOP18 [DX1033]
HR6P62P4YHL@SOP14 [DX1000]
HR6P62P4YHLD@SOP14 [DX1000]
HR6P67P4D [DX0001]
HR6P67P4DL [DX0001]
HR6P67P4DL-B [DX0001]
HR6P67P4DLR [DX0001]
HR6P67P4DLRB [DX0001]
HR6P67P4SL@SOP14 [DX1065]
HR6P67P4SL-B@SOP14 [DX1033]
HR6P67P4SLR@SOP14 [DX1065]
HR6P67P4SLRB@SOP14 [DX1033]
HR6P71F8D [DX0001]
HR6P71F8D(BOREN) [DX0001]
HR6P71F8D(BOREN)(ISP) [DX0001]
HR6P71F8D(ISP) [DX0001]
HR6P71F8D(REVERSE) [DX0001]
HR6P71F8S(BOREN)@SOP20 [DX1033]
HR6P71F8S(BOREN)@SOP20(ISP) [DX0001]
HR6P71F8S(REVERSE)@SOP20 [DX1033]
HR6P71F8S@SOP20 [DX1033]
HR6P71F8S@SOP20(ISP) [DX0001]

HR6P72P4D [DX0001]
HR6P72P4DL [DX0001]
HR6P72P4S@SOP28 [DX0001]
HR6P72P4SL@SOP28 [DX1033]
HR6P73P8DB [DX0001]
HR6P73P8DBL [DX0001]
HR6P73P8SB@SOP28 [DX1033]
HR6P73P8SBL@SOP28 [DX1033]
HR6P73PGD [DX0001]
HR6P73PGDH [DX0001]
HR6P73PGDHL [DX0001]
HR6P73PGS@SOP28 [DX1033]
HR6P73PGSH@SOP28 [DX1033]
HR6P73PGSHL@SOP28 [DX1033]
HR6P76PGD [DX0001]
HR6P76PGDL [DX0001]
HR6P76PGS@SOP28 [DX0001]
HR6P76PGSL@SOP28 [DX1033]
HR6P77PGD [DX0001]
HR6P77PGDL [DX0001]
HR6P77PGL@LQFP44 [DX3003]
HR6P77PGLL@LQFP44 [DX3005]
HR6P78P4SL@SOP32 [DX1069]
HR6P90FGD [DX0001]
HR6P90FGD(ISP) [DX0001]
HR6P90FGS@SOP28 [DX1033]
HR6P90FGS@SOP28(ISP) [DX0001]
HR6P90FHD [DX0001]
HR6P90FHD(ISP) [DX0001]
HR6P90FHS@SOP28 [DX1033]
HR6P90FHS@SOP28(ISP) [DX0001]
HR6P91FGS@SOP32 [DX1069]
HR6P91FGS@SOP32(ISP) [DX0001]
HR6P91FHS@SOP32 [DX1069]
HR6P91FHS@SOP32(ISP) [DX0001]
HR6P92FGD [DX0001]
HR6P92FGD(ISP) [DX0001]
HR6P92FGL@LQFP44 [DX3003]
HR6P92FGL@LQFP44(ISP) [DX0001]
HR6P92FHD [DX0001]
HR6P92FHD(ISP) [DX0001]
HR6P92FHL@LQFP44 [DX3003]
HR6P92FHL@LQFP44(ISP) [DX0001]
HR6P95F8D [DX0001]
HR6P95F8D(ISP) [DX0001]
HR6P95F8S@SOP28
HR6P95F8S@SOP28(ISP) [DX0001]
HR6P97FGD [DX0001]
HR6P97FGD(ISP) [DX0001]
HR6P97FGD-E [DX0001]
HR6P97FGD-E(ISP) [DX0001]
HR6P97FGS@SOP28 [DX1033]
HR6P97FGS@SOP28(ISP) [DX0001]
HR6P97FGS-E@SOP28 [DX1033]
HR6P97FGS-E@SOP28(ISP) [DX0001]
HR6P98FGD [DX0001]
HR6P98FGD(ISP) [DX0001]
HR6P98FGD-E [DX0001]
HR6P98FGD-E(ISP) [DX0001]
HR6P98FGL@LQFP44 [DX3003]
HR6P98FGL@LQFP44(ISP) [DX0001]
HR6P98FGL-E@LQFP44 [DX3003]
HR6P98FGL-E@LQFP44(ISP) [DX0001]
HR7P164P4D1L [DX0001]
HR7P164P4D2L [DX0001]
HR7P164P4D3L [DX0001]
HR7P164P4D4L [DX0001]
HR7P164P4RL@SSOP20 [DX1000]
HR7P164P4S1L@SOP20 [DX1033]
HR7P164P4S2L@SOP18 [DX1033]
HR7P164P4S3L@SOP16 [DX1033]
HR7P164P4S4L@SOP14 [DX1033]
HR7P169FGD [DX0001]
HR7P169FGD@ISP [DX0001]
HR7P169FGDD [DX0001]
HR7P169FGDD@ISP [DX0001]
HR7P169FGS [DX1033]
HR7P169FGS@ISP [DX0001]
HR7P169FGS3 [DX1016]
HR7P169FGS3@ISP [DX0001]
HR7P169FGS4 [DX1016]
HR7P169FGS4@ISP [DX0001]
HR7P169FGS5 [DX1045]
HR7P169FGS5@ISP [DX0001]
HR7P169FGTF [DX1000]
HR7P169FGTF@ISP [DX0001]
HR7P170FHD [DX0001]
HR7P170FHD@ISP [DX0001]
HR7P170FHS [DX1033]
HR7P170FHS@ISP [DX0001]
HR7P170FHS3 [DX1016]
HR7P170FHS3@ISP [DX0001]
HR7P170FHS4 [DX1016]
HR7P170FHS4@ISP [DX0001]
HR7P170FHS5 [DX1045]
HR7P170FHS5@ISP [DX0001]

HR7P171F8D1 [DX0001]
HR7P171F8D2 [DX0001]
HR7P171F8D3 [DX0001]
HR7P171F8D4 [DX0001]
HR7P171F8S1@SOP20 [DX1033]
HR7P171F8S2@SOP18 [DX1033]
HR7P171F8S3@SOP16 [DX1033]
HR7P171F8S4@SOP14 [DX1030]
HR7P187F4D1 [DX0001]
HR7P187F4D2 [DX0001]
HR7P187F4S1@SOP14 [DX1030]
HR7P187F4S2@SOP8 [DX1030]
HR7P192FLL1@ISP [DX0001]
HR7P192FLL1@LQFP44 [DX3003]
HR7P193FGD1 [DX0001]
HR7P193FGS@LQFP44 [DX3005]
HR7P193FGS@SOP28 [DX1033]
HR7P193FGS@SOP32 [DX1069]
HR7P193FGV [DX0001]
HR7P194FGD1 [DX0001]
HR7P194FGS@LQFP44 [DX3005]
HR7P194FGS@SOP28 [DX1033]
HR7P194FGS@SOP32 [DX1069]
HR7P194FGV [DX0001]
HR7P195F8D1 [DX0001]
HR7P195F8D2 [DX0001]
HR7P195F8R@SSOP20 [DX1074]
HR7P195F8S@SOP28 [DX1033]
HR7P195F8S2@SOP20 [DX1033]
HR7P195F8S3@SOP32 [DX1069]
HR7P195F8V [DX0001]
HR7P195FGD1 [DX0001]
HR7P195FGD2 [DX0001]
HR7P195FGR@SSOP20 [DX1074]
HR7P195FGS@SOP28 [DX1033]
HR7P195FGS2@SOP20 [DX1033]
HR7P195FGS3@SOP32 [DX1069]
HR7P195FGV [DX0001]
HR7P196FLL@ISP [DX0001]
HR7P196FLL@LQFP64 [DX3013]
HR7P196FLL1@ISP [DX0001]
HR7P196FLL1@LQFP80 [DX3060]
HR7P196FLL2@ISP [DX0001]
HR7P196FLL2@LQFP64 [DX3011]
HR7P201FHD [DX0001]
HR7P201FHD@ISP [DX0001]
HR7P201FHS [DX1033]
HR7P201FHS@ISP [DX0001]
HR7P201FHS3 [DX1016]
HR7P201FHS3@ISP [DX0001]
HR7P201FHS4 [DX1016]
HR7P201FHS4@ISP [DX0001]
HR7P201FHS5 [DX1045]
HR7P201FHS5@ISP [DX0001]
HR7P90FHD [DX0001]
HR7P90FHS@SOP28 [DX1033]
HR7P90FJD [DX0001]
HR7P90FJS@SOP28 [DX1033]
HR7P91FHL@LQFP32 [DX3001]
HR7P91FHS@SOP32 [DX1069]
HR7P91FHV [DX0001]
HR7P91FJL@LQFP32 [DX3001]
HR7P91FJS@SOP32 [DX1069]
HR7P91FJV [DX0001]
HR7P92FHL@LQFP44 [DX3005]
HR7P92FJL@LQFP44 [DX3005]
HR7T46P8V@SDIP42 [DX0042]
HR7T47P8L@LQFP44 [DX3003]
MC9S08AC16CFG [DX3107-1]
MC9S08AC16CFGE [DX3107-1]
MC9S08AC16CFJ [DX3109-1]
MC9S08AC16CFJE [DX3109-1]
MC9S08AC16MFG [DX3107-1]
MC9S08AC16MFGE [DX3107-1]
MC9S08AC16MFJ [DX3109-1]
MC9S08AC16MFJE [DX3109-1]
MC9S08AC16VFG [DX3107-1]
MC9S08AC16VFGE [DX3107-1]
MC9S08AC16VFJ [DX3109-1]
MC9S08AC16VFJE [DX3109-1]
MC9S08AC32CFG [DX3107-1]
MC9S08AC32CFGE [DX3107-1]
MC9S08AC32CFJ [DX3109-1]
MC9S08AC32CFJE [DX3109-1]
MC9S08AC32MFG [DX3107-1]
MC9S08AC32MFGE [DX3107-1]
MC9S08AC32MFJ [DX3109-1]
MC9S08AC32MFJE [DX3109-1]
MC9S08AC32VFG [DX3107-1]
MC9S08AC32VFGE [DX3107-1]
MC9S08AC32VFJ [DX3109-1]
MC9S08AC32VFJE [DX3109-1]
MC9S08AC48CFG [DX3107-1]
MC9S08AC48CFGE [DX3107-1]
MC9S08AC48CFJ [DX3109-1]
MC9S08AC48CFJE [DX3109-1]

MC9S08AC48MFG [DX3107-1]
MC9S08AC48MFGE [DX3107-1]
MC9S08AC48MFJ [DX3109-1]
MC9S08AC48MFJE [DX3109-1]
MC9S08AC48VFG [DX3107-1]
MC9S08AC48VFGE [DX3107-1]
MC9S08AC48VFJ [DX3109-1]
MC9S08AC48VFJE [DX3109-1]
MC9S08AC60CFG [DX3107-1]
MC9S08AC60CFGE [DX3107-1]
MC9S08AC60CFJ [DX3109-1]
MC9S08AC60CFJE [DX3109-1]
MC9S08AC60MFG [DX3107-1]
MC9S08AC60MFGE [DX3107-1]
MC9S08AC60MFJ [DX3109-1]
MC9S08AC60MFJE [DX3109-1]
MC9S08AC60VFG [DX3107-1]
MC9S08AC60VFGE [DX3107-1]
MC9S08AC60VFJ [DX3109-1]
MC9S08AC60VFJE [DX3109-1]
MC9S08AC8CFG [DX3107-1]
MC9S08AC8CFGE [DX3107-1]
MC9S08AC8CFJ [DX3109-1]
MC9S08AC8CFJE [DX3109-1]
MC9S08AC8MFG [DX3107-1]
MC9S08AC8MFGE [DX3107-1]
MC9S08AC8MFJ [DX3109-1]
MC9S08AC8MFJE [DX3109-1]
MC9S08AC8VFG [DX3107-1]
MC9S08AC8VFGE [DX3107-1]
MC9S08AC8VFJ [DX3109-1]
MC9S08AC8VFJE [DX3109-1]
MC9S08AW16CFG [DX3107-1]
MC9S08AW16CFGE [DX3107-1]
MC9S08AW16MFG [DX3107-1]
MC9S08AW16MFGE [DX3107-1]
MC9S08AW16VFG [DX3107-1]
MC9S08AW16VFGE [DX3107-1]
MC9S08AW32CFG [DX3107-1]
MC9S08AW32CFGE [DX3107-1]
MC9S08AW32MFG [DX3107-1]
MC9S08AW32MFGE [DX3107-1]
MC9S08AW32VFG [DX3107-1]
MC9S08AW32VFGE [DX3107-1]
MC9S08AW48CFG [DX3107-1]
MC9S08AW48CFGE [DX3107-1]
MC9S08AW48MFG [DX3107-1]
MC9S08AW48MFGE [DX3107-1]
MC9S08AW48VFG [DX3107-1]
MC9S08AW48VFGE [DX3107-1]
MC9S08AW60CFG [DX3107-1]
MC9S08AW60CFGE [DX3107-1]
MC9S08AW60MFG [DX3107-1]
MC9S08AW60MFGE [DX3107-1]
MC9S08AW60VFG [DX3107-1]
MC9S08AW60VFGE [DX3107-1]
S9S08AW16ACLM [DX3109-1]
S9S08AW16ACLS [DX3107-1]
S9S08AW16AMLM [DX3109-1]
S9S08AW16AMLS [DX3107-1]
S9S08AW16AVLM [DX3109-1]
S9S08AW16AVLS [DX3107-1]
S9S08AW8ACLM [DX3109-1]
S9S08AW8ACLS [DX3107-1]
S9S08AW8AMLM [DX3109-1]
S9S08AW8AMLS [DX3107-1]
S9S08AW8AVLM [DX3109-1]
S9S08AW8AVLS [DX3107-1]
SH67P33 [DX0001]
SH67P33@SOIC20 [DX1033]
SH67P33@SSOP20 [DX1067]
SH67P33C [DX0001]
SH67P33C@SOIC20 [DX1033]
SH67P33C@SSOP20 [DX1067]

HARRIS

E(E)PROM/FRAM/NVRAM

HM-6616 [DX0001]
M1-6617/883 [DX0001]

BPROM

7610A [DX0001]
7611A [DX0001]

DRAM & SRAM

HM65642 [DX0001]
HM65642@TSOP28 [DX1001]

HIKVISION

E(E)PROM/FRAM/NVRAM

N25Q512A13GSF40F [DX1033#1]

HIMAX

MICROCONTROLLER

HX8915@QFN32 [DX4015]

HITACHI

E(E)PROM/FRAM/NVRAM

HN27128AG [DX0001]
HN27128AP [DX0001]
HN27256G [DX0001]
HN27256P [DX0001]
HN27512G [DX0001]
HN27512P [DX0001]
HN27C101AG [DX0001]
HN27C101AP [DX0001]
HN27C101G [DX0001]
HN27C101P [DX0001]
HN27C1024HG [DX0001]
HN27C1024HG@PLCC44 [DX2044]
HN27C256AG [DX0001]
HN27C256FP [DX0001]
HN27C256G [DX0001]
HN27C256HG [DX0001]
HN27C301AG [DX0001]
HN27C301AP [DX0001]
HN27C301G [DX0001]
HN27C301P [DX0001]
HN27C4000FP [DX0001]
HN27C4000G [DX0001]
HN27C4001 [DX0001]
HN27C4001@TSOP32 [DX1002]
HN27C4001G [DX0001]
HN27C4096A [DX0001]
HN27C4096A@PLCC44 [DX2044]
HN27C4096FP [DX0001]
HN27C4096FP@PLCC44 [DX2044]
HN27C4096G [DX0001]
HN27C4096G@PLCC44 [DX2044]
HN27C512G [DX0001]
HN27C512G@PLCC32 [DX2032]
HN27C64G [DX0001]
HN28F101 [DX0001]
HN28F101(REVERSE)@TSOP32 [DX1002]
HN28F101@PLCC32 [DX2032]
HN28F101@SOP32 [DX1019]
HN28F101@TSOP32 [DX1002]
HN462716G [DX0001]
HN462732G [DX0001]
HN48016
HN48016P
HN4827128G [DX0001]

HN4827128P [DX0001]
HN482732AG [DX0001]
HN482764G [DX0001]
HN482764P [DX0001]
HN58064(FP)@SOIC28 [DX1033]
HN58064(P) [DX0001]
HN58C1001(FP)@SSOP32 [DX1020]
HN58C1001(P) [DX0001]
HN58C1001(T)@VSOP32 [DX1003]
HN58C256 [DX0001]
HN58C256A(FP)@SOP28 [DX1033]
HN58C256A(P) [DX0001]
HN58C256A(T)@TSOP28 [DX1024]
HN58C256FP@SOIC28 [DX1018]
HN58C257A(T)@TSOP32 [DX1003]
HN58C65(FP)@SOIC28 [DX1033]
HN58C65(P) [DX0001]
HN58V24256 [DX0001]
HN58V24256@SOIC8 [DX1045]
HN58V24256@TSSOP14 [DX1000]
HN58V24512 [DX0001]
HN58V24512@SOIC8 [DX1045]
HN58V256A [DX0001]
HN58V256A@TSOP28 [DX1024]
HN58V65A [DX0001]
HN58V65A@SOIC28 [DX1064]
HN58V65A@TSOP28 [DX1024]
HN58V66A [DX0001]
HN58V66A@SOIC28 [DX1033]
HN58V66A@TSOP28 [DX1024]
HN58W241000 [DX0001]
HN58W241000@SOIC8[150mil] [DX1045]
HN58W241000@SOIC8[200mil] [DX1044]
HN58X2402 [DX0001]
HN58X2402@SOIC8 [DX1045]
HN58X2402@TSSOP8 [DX1059]
HN58X2404 [DX0001]
HN58X2404@SOIC8 [DX1045]
HN58X2404@TSSOP8 [DX1059]
HN58X2408 [DX0001]
HN58X2408@SOIC8 [DX1045]
HN58X2408@TSSOP8 [DX1059]
HN58X24128 [DX0001]
HN58X24128@SOIC8 [DX1045]
HN58X2416 [DX0001]
HN58X2416@SOIC8 [DX1045]
HN58X2416@TSSOP8 [DX1059]
HN58X24256 [DX0001]
HN58X24256@SOIC8 [DX1045]
HN58X2432 [DX0001]
HN58X2432@SOIC8 [DX1045]
HN58X2432@TSSOP8 [DX1059]
HN58X24512 [DX0001]
HN58X24512@SOIC8 [DX1045]
HN58X2464 [DX0001]
HN58X2464@SOIC8 [DX1045]
HN58X2464@TSSOP8 [DX1059]
HN58X2502@SOIC8 [DX1045]
HN58X2502@TSSOP8 [DX1059]
HN58X2504@SOIC8 [DX1045]
HN58X2504@TSSOP8 [DX1059]
HN58X25128@SOIC8 [DX1045]
HN58X25128@TSSOP14 [DX1000]
HN58X25256@SOIC8 [DX1045]
HN58X25256@TSSOP14 [DX1000]
HN58X2532@SOIC8 [DX1045]
HN58X2532@TSSOP8 [DX1059]
HN58X2564@SOIC8 [DX1045]
HN58X2564@TSSOP8 [DX1059]
HT29VB800@TSOP48 [DX1043]
HT29VT800@TSOP48 [DX1043]
HT29WB800@TSOP48 [DX1043]
HT29WT800@TSOP48 [DX1043]

DRAM & SRAM

HM62256 [DX0001]
HM62256@TSOP28 [DX1001]
HM62256B [DX0001]
HM62256B@TSOP28 [DX1001]
HM6264A [DX0001]
HM6264A@TSOP28 [DX1001]
HM628128 [DX0001]
HM628128@TSOP32 [DX1002]
HM628128A [DX0001]
HM628128A@TSOP32 [DX1002]
HM62832 [DX0001]
HM62832@TSOP28 [DX1001]

HM62832H [DX0001]
HM628512 [DX0001]
HM65256B [DX0001]
HM658128 [DX0001]
HM66204 [DX0001]
HM62832H@TSOP28 [DX1001]
HM628512@TSOP32 [DX1002]
HM65256B@TSOP28 [DX1001]
HM658128@TSOP32 [DX1002]
HM66204@TSOP32 [DX1002]

MICROCONTROLLER

HD63701V0C [DX0001]
HD63701X0C@SDIP64 [DX0064]
HD63701Y0 [DX0001]
HD63701Y0C@SDIP64 [DX0064]
HD63705V0 [DX0001]
HD637A01V0C [DX0001]
HD637A01X0C@SDIP64 [DX0064]
HD637A01Y0C@SDIP64 [DX0064]
HD637A05V0 [DX0001]
HD637B01V0C [DX0001]
HD637B01X0C@SDIP64 [DX0064]
HD637B01Y0C@SDIP64 [DX0064]
HD637B05V0 [DX0001]
HD6472246FA@QFP100 [DX3043]
HD6472357TE@QFP120 [DX3027]
HD6472655TE@QFP120 [DX3027]
HD6472655VTE@QFP120 [DX3027]
HD6473032TF@QFP80 [DX3016]
HD6473042TF@TQFP100 [DX3043]
HD6473042VTF@TQFP100 [DX3043]
HD6473228F@QFP64 [DX3014]
HD6473238CP@PLCC68 [DX2068]
HD6473238P@SDIP64 [DX0064]
HD6473256F@QFP64 [DX3014]
HD6473257C@SDIP64 [DX0064]
HD6473257F@QFP64 [DX3014]
HD6473258C@SDIP64 [DX0064]
HD6473258F@QFP64 [DX3014]
HD6473308CG@PLCC84 [DX2084]
HD6473308F@QFP80 [DX3018]
HD6473334YF@QFP80 [DX3018]
HD6473337YCG@PLCC84 [DX2084]
HD6473337YF@QFP80 [DX3018]
HD6473378CP@PLCC84 [DX2084]
HD6473644RH [DX3014]
HD64738024H@QFP80 [DX3018]
HD6473834D@QFP100 [DX3043]
HD6473834F@PQFP100 [DX3023]
HD6473834X@QFP100 [DX3043]
HD63701V0P [DX0001]
HD63701X0P@SDIP64 [DX0064]
HD63701Y0C [DX0001]
HD63701Y0P@SDIP64 [DX0064]
HD63705V0C [DX0001]
HD637A01V0P [DX0001]
HD637A01X0P@SDIP64 [DX0064]
HD637A01Y0P@SDIP64 [DX0064]
HD637A05V0C [DX0001]
HD637B01V0P [DX0001]
HD637B01X0P@SDIP64 [DX0064]
HD637B01Y0P@SDIP64 [DX0064]
HD637B05V0C [DX0001]
HD6472357F@PQFP128 [DX3031]
HD6472655F@PQFP128 [DX3031]
HD6472655VF@PQFP128 [DX3031]
HD6473032F@QFP80 [DX3018]
HD6473042F@QFP100 [DX3043]
HD6473042VF@QFP100 [DX3043]
HD6473228CP@PLCC68 [DX2068]
HD6473228P@SDIP64 [DX0064]
HD6473238F@QFP64 [DX3014]
HD6473256CP@PLCC68 [DX2068]
HD6473256P@SDIP64 [DX0064]
HD6473257CP@PLCC68 [DX2068]
HD6473257P@SDIP64 [DX0064]
HD6473258CP@PLCC68 [DX2068]
HD6473258P@SDIP64 [DX0064]
HD6473308CP@PLCC84 [DX2084]
HD6473334YCP@PLCC84 [DX2084]
HD6473334YTF@QFP80 [DX3016]
HD6473337YCP@PLCC84 [DX2084]
HD6473337YTF@QFP80 [DX3016]
HD6473644H [DX3014]
HD64738024F@PQFP80 [DX3019]
HD64738024W@QFP80 [DX3016]
HD6473834E@PQFP100 [DX3023]
HD6473834H@QFP100 [DX3043]
HD6473837D@QFP100 [DX3043]

HD6473837E@PQFP100 [DX3023]
HD6473837F@PQFP100 [DX3023]
HD6473837H@QFP100 [DX3043]
HD6473837X@QFP100 [DX3043]
HD6473877H@QFP100 [DX3043]
HD6475208C@SDIP64 [DX0064]
HD6475208P@SDIP64 [DX0064]
HD6475328CG@PLCC84 [DX2084]
HD6475328CP@PLCC84 [DX2084]
HD6475328F@QFP80 [DX3018]
HD6475348CG@PLCC84 [DX2084]
HD6475348CP@PLCC84 [DX2084]
HD6475348F@QFP80 [DX3018]
HD6475348RCG@PLCC84 [DX2084]
HD6475348RCP@PLCC84 [DX2084]
HD6475348RF@QFP80 [DX3018]
HD6475348SCG@PLCC84 [DX2084]
HD6475348SCP@PLCC84 [DX2084]
HD6475348SF@QFP80 [DX3018]
HD6475368CG@PLCC84 [DX2084]
HD6475368CP@PLCC84 [DX2084]
HD6475368F@QFP80 [DX3018]
HD6475368RCG@PLCC84 [DX2084]
HD6475368RCP@PLCC84 [DX2084]
HD6475368RF@QFP80 [DX3018]
HD6475368SCG@PLCC84 [DX2084]
HD6475368SCP@PLCC84 [DX2084]
HD6475368SF@QFP80 [DX3018]
HD6475708F [DX3025]
HD6477034F@QFP112 [DX3025]
HD6477042F@QFP112 [DX3025]
HD6477043F@QFP144 [DX3035]
HD64F2110BFA@QFP100 [DX3021]
HD64F2110BTE@QFP100 [DX3021]
HD64F2110BVFA@QFP100 [DX3021]
HD64F2110BVTE@QFP100 [DX3021]
HD64F2111BVTE@QFP144 [DX3041]
HD64F2132RFA20@QFP80 [DX3018]
HD64F2132RTF10@QFP80 [DX3016]
HD64F2132RVFA10@QFP80 [DX3018]
HD64F2132RVTF10@QFP80 [DX3016]
HD64F2134AFA20@QFP80 [DX3018]
HD64F2134ATF10@QFP80 [DX3016]
HD64F2134AVFA10@QFP80 [DX3018]
HD64F2134AVTF10@QFP80 [DX3016]
HD64F2134FA20@QFP80 [DX3018]
HD64F2134TF10@QFP80 [DX3016]
HD64F2134VFA10@QFP80 [DX3018]
HD64F2134VTF10@QFP80 [DX3016]
HD64F2138AFA20@QFP80 [DX3018]
HD64F2138ATF10@QFP80 [DX3016]
HD64F2138AVFA10@QFP80 [DX3018]
HD64F2138AVTF10@QFP80 [DX3016]
HD64F2138FA20@QFP80 [DX3018]
HD64F2138TF10@QFP80 [DX3016]
HD64F2138VFA10@QFP80 [DX3018]
HD64F2138VTF10@QFP80 [DX3016]
HD64F2140BVFA10@QFP100 [DX3021]
HD64F2140BVTE10@QFP100 [DX3021]
HD64F2141BVFA10@QFP100 [DX3021]
HD64F2141BVTE10@QFP100 [DX3021]
HD64F2142RFA20@QFP100 [DX3021]
HD64F2142RTE20@QFP100 [DX3021]
HD64F2142RVFA10@QFP100 [DX3021]
HD64F2142RVTE10@QFP100 [DX3021]
HD64F2144AFA20@QFP100 [DX3021]
HD64F2144ATE20@QFP100 [DX3021]
HD64F2144AVFA10@QFP100 [DX3021]
HD64F2144AVTE10@QFP100 [DX3021]
HD64F2144FA20@QFP100 [DX3021]
HD64F2144TE20@QFP100 [DX3021]
HD64F2144VFA10@QFP100 [DX3021]
HD64F2144VTE10@QFP100 [DX3021]
HD64F2145BVFA10@QFP100 [DX3021]
HD64F2145BVTE10@QFP100 [DX3021]
HD64F2147AFA20@QFP100 [DX3021]
HD64F2147ATE20@QFP100 [DX3021]
HD64F2147AVFA10@QFP100 [DX3021]
HD64F2147AVTE10@QFP100 [DX3021]
HD64F2147NFA20@QFP100 [DX3021]
HD64F2147NTE20@QFP100 [DX3021]
HD64F2147NVFA10@QFP100 [DX3021]
HD64F2147NVTE10@QFP100 [DX3021]
HD64F2148AFA20@QFP100 [DX3021]
HD64F2148ATE20@QFP100 [DX3021]
HD64F2148AVFA10@QFP100 [DX3021]
HD64F2148AVTE10@QFP100 [DX3021]
HD64F2148BFA20@QFP100 [DX3021]
HD64F2148BTE20@QFP100 [DX3021]
HD64F2148BVFA10@QFP100 [DX3021]
HD64F2148BVTE10@QFP100 [DX3021]
HD64F2148FA20@QFP100 [DX3021]
HD64F2148TE20@QFP100 [DX3021]
HD64F2148VFA10@QFP100 [DX3021]
HD64F2148VTE10@QFP100 [DX3021]
HD64F2149YFA20@QFP100 [DX3021]

HD64F2149YTE20@QFP100 [DX3021]
HD64F2149YVFA10@QFP100 [DX3021]
HD64F2149YVTE10@QFP100 [DX3021]
HD64F2160BTE20@QFP144 [DX3041]
HD64F2160BVTE10@QFP144 [DX3041]
HD64F2161BTE20@QFP144 [DX3041]
HD64F2161BVTE10@QFP144 [DX3041]
HD64F2166VTE33@TQFP144 [DX3034]
HD64F2167VTE33@TQFP144 [DX3034]
HD64F2168VTE33@TQFP144 [DX3034]
HD64F2169YTE20@QFP144 [DX3041]
HD64F2169YVTE10@QFP144 [DX3041]
HD64F2177VTE33@TQFP144 [DX3034]
HD64F2210CUFP [DX3011]
HD64F2210FP [DX3011]
HD64F2210UFP [DX3011]
HD64F2211CUFP [DX3011]
HD64F2211FP [DX3011]
HD64F2211UFP [DX3011]
HD64F2212CUFP [DX3011]
HD64F2212FP [DX3011]
HD64F2212UFP [DX3011]
HD64F2215RTE@QFP120 [DX3027]
HD64F2215RUTE@QFP120 [DX3027]
HD64F2215TE@QFP120 [DX3027]
HD64F2215TTE@QFP120 [DX3027]
HD64F2215TUTE@QFP120 [DX3027]
HD64F2215UTE@QFP120 [DX3027]
HD64F2218TF@QFP100 [DX3071]
HD64F2218UTF@QFP100 [DX3071]
HD64F2238ATE@TQFP100 [DX3043]
HD64F2238BF@PQFP100 [DX3022]
HD64F2238BFA@QFP100 [DX3043]
HD64F2238BTE@TQFP100 [DX3043]
HD64F2238BTF@TQFP100 [DX3071]
HD64F2238RBQ@FBGA112 [DX5058]
HD64F2238RBR@FBGA112 [DX5058]
HD64F2238RF@PQFP100 [DX3022]
HD64F2238RFA@QFP100 [DX3043]
HD64F2238RTE@TQFP100 [DX3043]
HD64F2238RTF@TQFP100 [DX3071]
HD64F2239BQ@FBGA112 [DX5058]
HD64F2239F@PQFP100 [DX3022]
HD64F2239FA@QFP100 [DX3043]
HD64F2239TE@TQFP100 [DX3043]
HD64F2239TF@TQFP100 [DX3071]
HD64F2258F@PQFP100 [DX3022]
HD64F2258FA@QFP100 [DX3043]
HD64F2258TE@TQFP100 [DX3043]
HD64F2265FA@TQFP100 [DX3043]
HD64F2265TE@TQFP100 [DX3043]
HD64F2265TF@TQFP100 [DX3071]
HD64F2266FA@TQFP100 [DX3043]
HD64F2266TE@TQFP100 [DX3043]
HD64F2266TF@TQFP100 [DX3071]
HD64F2268FA@TQFP100 [DX3043]
HD64F2268TE@TQFP100 [DX3043]
HD64F2268TF@TQFP100 [DX3071]
HD64F2280F20B@QFP100 [DX3022]
HD64F2280F20RB@QFP100 [DX3022]
HD64F2282F20@QFP100 [DX3022]
HD64F2314VF@PQFP100 [DX3022]
HD64F2314VTE@QFP100 [DX3043]
HD64F2315VF@PQFP100 [DX3022]
HD64F2315VTE@QFP100 [DX3043]
HD64F2317VF@PQFP100 [DX3022]
HD64F2317VTE@QFP100 [DX3043]
HD64F2317VTF@QFP100 [DX3043]
HD64F2318VF@PQFP100 [DX3022]
HD64F2318VTE@QFP100 [DX3043]
HD64F2318VTF@QFP100 [DX3043]
HD64F2319EVF@PQFP100 [DX3022]
HD64F2319EVTE@QFP100 [DX3043]
HD64F2319VF@PQFP100 [DX3022]
HD64F2319VTE@QFP100 [DX3043]
HD64F2326VF@PQFP128 [DX3032]
HD64F2326VTE@QFP120 [DX3027]
HD64F2328BVF@PQFP128 [DX3032]
HD64F2328BVTE@QFP120 [DX3027]
HD64F2329BVF@PQFP128 [DX3032]
HD64F2329BVTE@QFP120 [DX3027]
HD64F2329EVF@PQFP128 [DX3032]
HD64F2329EVTE@QFP120 [DX3027]
HD64F2338VFC@QFP144 [DX3035]
HD64F2339EVFC@QFP144 [DX3035]
HD64F2339VFC@QFP144 [DX3035]
HD64F2345F@PQFP100 [DX3022]
HD64F2345FA@QFP100 [DX3043]
HD64F2345TE@QFP100 [DX3043]
HD64F2345TF@QFP100 [DX3071]
HD64F2357F@PQFP128 [DX3032]
HD64F2357TE@QFP120 [DX3027]
HD64F2360VTE@QFP120 [DX3030]
HD64F2361VTE@QFP120 [DX3030]
HD64F2362VTE@QFP120 [DX3030]
HD64F2364VTE@QFP120 [DX3030]

HD64F2368VTE@QFP120 [DX3030]
HD64F2370RVFQ@QFP144 [DX3035]
HD64F2370VFQ@QFP144 [DX3035]
HD64F2371RVFQ@QFP144 [DX3035]
HD64F2371VFQ@QFP144 [DX3035]
HD64F2372RVFQ@QFP144 [DX3035]
HD64F2372VFQ@QFP144 [DX3035]
HD64F2374RVFQ@QFP144 [DX3035]
HD64F2374VFQ@QFP144 [DX3035]
HD64F2376VFQ@QFP144 [DX3035]
HD64F2377RVFQ@QFP144 [DX3035]
HD64F2377VFQ@QFP144 [DX3035]
HD64F2378BVFQ@QFP144 [DX3035]
HD64F2378RVFQ@QFP144 [DX3035]
HD64F2398F@PQFP128 [DX3032]
HD64F2398FT@PQFP128 [DX3032]
HD64F2398TE@QFP120 [DX3027]
HD64F2398TET@QFP120 [DX3027]
HD64F2505FC26@QFP144 [DX3051]
HD64F2506FC26@QFP144 [DX3051]
HD64F2551FC26@QFP144 [DX3051]
HD64F2552FC26@QFP144 [DX3051]
HD64F2556FC20@QFP144 [DX3051]
HD64F2612FA20@QFP80 [DX3018]
HD64F2615F20@QFP80 [DX3018]
HD64F2615F24@QFP80 [DX3018]
HD64F2623FA@QFP100 [DX3043]
HD64F2626FA@QFP100 [DX3043]
HD64F2628FA@QFP100 [DX3043]
HD64F2630F@PQFP128 [DX3032]
HD64F2630UF@PQFP128 [DX3032]
HD64F2630WF@PQFP128 [DX3032]
HD64F2633F@PQFP128 [DX3032]
HD64F2633RF@PQFP128 [DX3032]
HD64F2633RTE@QFP120 [DX3027]
HD64F2633TE@QFP120 [DX3027]
HD64F2635F@PQFP128 [DX3032]
HD64F2636F@PQFP128 [DX3032]
HD64F2636UF@PQFP128 [DX3032]
HD64F2638F@PQFP128 [DX3032]
HD64F2638UF@PQFP128 [DX3032]
HD64F2638WF@PQFP128 [DX3032]
HD64F2639UF@PQFP128 [DX3032]
HD64F2639WF@PQFP128 [DX3032]
HD64F2643FC25@QFP144 [DX3035]
HD64F2646RFC20@QFP144 [DX3035]
HD64F2648RFC20@QFP144 [DX3035]
HD64F2649FC20@QFP144 [DX3035]
HD64F2667VFQ33@QFP144 [DX3035]
HD64F2676VF@QFP144 [DX3035]
HD64F3024F@TQFP100 [DX3021]
HD64F3024FP@PQFP100 [DX3022]
HD64F3024TE@TQFP100 [DX3021]
HD64F3026F@QFP100 [DX3021]
HD64F3026FP@PQFP100 [DX3022]
HD64F3026TE@TQFP100 [DX3021]
HD64F3029F@QFP100 [DX3043]
HD64F3029TE@TQFP100 [DX3043]
HD64F3039F@QFP80 [DX3018]
HD64F3039TE@TQFP80 [DX3016]
HD64F3039VF@QFP80 [DX3018]
HD64F3039VTE@TQFP80 [DX3016]
HD64F3048BF@TQFP100 [DX3021]
HD64F3048BTE@TQFP100 [DX3021]
HD64F3048BVF@TQFP100 [DX3021]
HD64F3048BVTE@TQFP100 [DX3021]
HD64F3048F@TQFP100 [DX3021]
HD64F3048TF@TQFP100 [DX3021]
HD64F3048VF@TQFP100 [DX3021]
HD64F3048VTF@TQFP100 [DX3021]
HD64F3052BF@TQFP100 [DX3021]
HD64F3052BTE@TQFP100 [DX3021]
HD64F3052BVF@TQFP100 [DX3021]
HD64F3052BVTE@TQFP100 [DX3021]
HD64F3052F@TQFP100 [DX3021]
HD64F3052TE@TQFP100 [DX3021]
HD64F3062BF@TQFP100 [DX3021]
HD64F3062BFP@PQFP100 [DX3022]
HD64F3062BTE@TQFP100 [DX3021]
HD64F3062F@TQFP100 [DX3021]
HD64F3062FP@PQFP100 [DX3022]
HD64F3062RF@TQFP100 [DX3021]
HD64F3062RFP@PQFP100 [DX3022]
HD64F3062RTE@TQFP100 [DX3021]
HD64F3062RVF@TQFP100 [DX3021]
HD64F3062RVFP@PQFP100 [DX3022]
HD64F3062RVTE@TQFP100 [DX3021]
HD64F3062TE@TQFP100 [DX3021]
HD64F3062VF@TQFP100 [DX3021]
HD64F3062VFP@TQFP100 [DX3022]
HD64F3062VTE@TQFP100 [DX3021]
HD64F3064BF@TQFP100 [DX3021]
HD64F3064BFP@PQFP100 [DX3022]
HD64F3064BTE@TQFP100 [DX3021]
HD64F3064F@TQFP100 [DX3021]
HD64F3064FP@PQFP100 [DX3022]

HD64F3064TE@TQFP100 [DX3021]
HD64F3067F@TQFP100 [DX3021]
HD64F3067FP@PQFP100 [DX3022]
HD64F3067RF@TQFP100 [DX3021]
HD64F3067RFP@PQFP100 [DX3022]
HD64F3067RTE@TQFP100 [DX3021]
HD64F3067RVF@TQFP100 [DX3021]
HD64F3067RVFP@PQFP100 [DX3022]
HD64F3067RVTE@TQFP100 [DX3021]
HD64F3067TE@TQFP100 [DX3021]
HD64F3067VF@TQFP100 [DX3021]
HD64F3067VFP@TQFP100 [DX3022]
HD64F3067VTE@TQFP100 [DX3021]
HD64F3068F@TQFP100 [DX3021]
HD64F3068TE@TQFP100 [DX3021]
HD64F3069F@TQFP100 [DX3043]
HD64F3069TE@TQFP100 [DX3043]
HD64F3334YCP@PLCC84 [DX2084]
HD64F3334YF@TQFP80 [DX3018]
HD64F3334YFLH@TQFP80 [DX3018]
HD64F3334YTF@TQFP80 [DX3016]
HD64F3334YTFLH@TQFP80 [DX3016]
HD64F3337YCP@PLCC84 [DX2084]
HD64F3337YF@TQFP80 [DX3018]
HD64F3337YFLH@TQFP80 [DX3018]
HD64F3337YTF@TQFP80 [DX3016]
HD64F3337YTFLH@TQFP80 [DX3016]
HD64F3394YCP@PLCC84 [DX2084]
HD64F3394YF@TQFP80 [DX3018]
HD64F3394YFLH@TQFP80 [DX3018]
HD64F3394YTF@TQFP80 [DX3016]
HD64F3394YTFLH@TQFP80 [DX3016]
HD64F3397CP@PLCC84 [DX2084]
HD64F3397F@TQFP80 [DX3018]
HD64F3397FLH@TQFP80 [DX3018]
HD64F3397TF@TQFP80 [DX3016]
HD64F3397TFLH@TQFP80 [DX3016]
HD64F3434F@TQFP100 [DX3021]
HD64F3434FLH@TQFP100 [DX3021]
HD64F3434TF@TQFP100 [DX3021]
HD64F3434TFLH@TQFP100 [DX3021]
HD64F3437F@TQFP100 [DX3021]
HD64F3437FLH@TQFP100 [DX3021]
HD64F3437TF@TQFP100 [DX3021]
HD64F3437TFLH@TQFP100 [DX3021]
HD64F36012FP@QFP64 [DX3011]
HD64F36012FT@QFN48 [DX4021]
HD64F36012FX@QFP48 [DX3008]
HD64F36012FY@QFP48 [DX3007]
HD64F36012GFP@QFP64 [DX3011]
HD64F36012GFT@QFN48 [DX4021]
HD64F36012GFX@QFP48 [DX3008]
HD64F36012GFY@QFP48 [DX3007]
HD64F36014FP@QFP64 [DX3011]
HD64F36014FT@QFN48 [DX4021]
HD64F36014FX@QFP48 [DX3008]
HD64F36014FY@QFP48 [DX3007]
HD64F36014GFP@QFP64 [DX3011]
HD64F36014GFT@QFN48 [DX4021]
HD64F36014GFX@QFP48 [DX3008]
HD64F36014GFY@QFP48 [DX3007]
HD64F36022FP@QFP64 [DX3011]
HD64F36022FT@QFN48 [DX4021]
HD64F36022FX@QFP48 [DX3008]
HD64F36022FY@QFP48 [DX3007]
HD64F36022GFP@QFP64 [DX3011]
HD64F36022GFT@QFN48 [DX4021]
HD64F36022GFX@QFP48 [DX3008]
HD64F36022GFY@QFP48 [DX3007]
HD64F36024FP@QFP64 [DX3011]
HD64F36024FT@QFN48 [DX4021]
HD64F36024FX@QFP48 [DX3008]
HD64F36024FY@QFP48 [DX3007]
HD64F36024GFP@QFP64 [DX3011]
HD64F36024GFT@QFN48 [DX4021]
HD64F36024GFX@QFP48 [DX3008]
HD64F36024GFY@QFP48 [DX3007]
HD64F36034FZ@QFP64 [DX3011]
HD64F36034GFZ@QFP64 [DX3011]
HD64F36034GH@QFP64 [DX3014]
HD64F36034H@QFP64 [DX3014]
HD64F36037FZ@QFP64 [DX3011]
HD64F36037GFZ@QFP64 [DX3011]
HD64F36037GH@QFP64 [DX3014]
HD64F36037H@QFP64 [DX3014]
HD64F36049GH@QFP80 [DX3018]
HD64F36049H@QFP80 [DX3018]
HD64F36054FZ@QFP64 [DX3011]
HD64F36054GFZ@QFP64 [DX3011]
HD64F36054GH@QFP64 [DX3014]
HD64F36054H@QFP64 [DX3014]
HD64F36057FZ@QFP64 [DX3011]
HD64F36057GFZ@QFP64 [DX3011]
HD64F36057GH@QFP64 [DX3014]
HD64F36057H@QFP64 [DX3014]
HD64F36064FP@QFP64 [DX3011]

HD64F36064GFP@QFP64 [DX3011]
HD64F36064GH@QFP64 [DX3014]
HD64F36064H@QFP64 [DX3014]
HD64F36074GFZ@QFP64 [DX3011]
HD64F36074GFZW@QFP64 [DX3011]
HD64F36074GH@QFP64 [DX3014]
HD64F36074GHV@QFP64 [DX3014]
HD64F36074GHW@QFP64 [DX3014]
HD64F36074GHZ@QFP64 [DX3014]
HD64F36074GHZW@QFP64 [DX3014]
HD64F36074LFZ@QFP64 [DX3011]
HD64F36074LFZW@QFP64 [DX3011]
HD64F36074LH@QFP64 [DX3014]
HD64F36074LHV@QFP64 [DX3014]
HD64F36074LHW@QFP64 [DX3014]
HD64F36074LHZ@QFP64 [DX3014]
HD64F36074LHZW@QFP64 [DX3014]
HD64F36077GFZ@QFP64 [DX3011]
HD64F36077GFZW@QFP64 [DX3011]
HD64F36077GH@QFP64 [DX3014]
HD64F36077GHV@QFP64 [DX3014]
HD64F36077GHW@QFP64 [DX3014]
HD64F36077GHZ@QFP64 [DX3014]
HD64F36077GHZW@QFP64 [DX3014]
HD64F36077LFZ@QFP64 [DX3011]
HD64F36077LFZW@QFP64 [DX3011]
HD64F36077LH@QFP64 [DX3014]
HD64F36077LHV@QFP64 [DX3014]
HD64F36077LHW@QFP64 [DX3014]
HD64F36077LHZ@QFP64 [DX3014]
HD64F36077LHZW@QFP64 [DX3014]
HD64F36078GFZ@QFP64 [DX3011]
HD64F36078GFZW@QFP64 [DX3011]
HD64F36078GH@QFP64 [DX3014]
HD64F36078GHV@QFP64 [DX3014]
HD64F36078GHW@QFP64 [DX3014]
HD64F36078GHZ@QFP64 [DX3014]
HD64F36078GHZW@QFP64 [DX3014]
HD64F36078LFZ@QFP64 [DX3011]
HD64F36078LFZW@QFP64 [DX3011]
HD64F36078LH@QFP64 [DX3014]
HD64F36078LHV@QFP64 [DX3014]
HD64F36078LHW@QFP64 [DX3014]
HD64F36078LHZ@QFP64 [DX3014]
HD64F36078LHZW@QFP64 [DX3014]
HD64F36079GFZ@QFP64 [DX3011]
HD64F36079GFZW@QFP64 [DX3011]
HD64F36079GH@QFP64 [DX3014]
HD64F36079GHV@QFP64 [DX3014]
HD64F36079GHW@QFP64 [DX3014]
HD64F36079GHZ@QFP64 [DX3014]
HD64F36079GHZW@QFP64 [DX3014]
HD64F36079LFZ@QFP64 [DX3011]
HD64F36079LFZW@QFP64 [DX3011]
HD64F36079LH@QFP64 [DX3014]
HD64F36079LHV@QFP64 [DX3014]
HD64F36079LHW@QFP64 [DX3014]
HD64F36079LHZ@QFP64 [DX3014]
HD64F36079LHZW@QFP64 [DX3014]
HD64F36087FP@QFP64 [DX3011]
HD64F36087H@QFP64 [DX3014]
HD64F36109F@PQFP100 [DX3022]
HD64F36109GF@PQFP100 [DX3022]
HD64F36109GH@LQFP100 [DX3043]
HD64F36109H@LQFP100 [DX3043]
HD64F3642AH@TQFP64 [DX3014]
HD64F3642AP@SDIP64 [DX0064]
HD64F3642AW@TQFP80 [DX3016]
HD64F3643H@TQFP64 [DX3014]
HD64F3643P@SDIP64 [DX0064]
HD64F3643W@TQFP80 [DX3016]
HD64F3644H@TQFP64 [DX3014]
HD64F3644P@SDIP64 [DX0064]
HD64F3644W@TQFP80 [DX3016]
HD64F3664BP@SDIP42 [DX0042]
HD64F3664FP@QFP64 [DX3011]
HD64F3664FX@QFP48 [DX3008]
HD64F3664FY@QFP48 [DX3007]
HD64F3664GBP@SDIP42 [DX0042]
HD64F3664GFP@QFP64 [DX3011]
HD64F3664GFX@QFP48 [DX3008]
HD64F3664GFY@QFP48 [DX3007]
HD64F3664GH@QFP64 [DX3014]
HD64F3664H@QFP64 [DX3014]
HD64F3684FP@QFP64 [DX3011]
HD64F3684GFP@QFP64 [DX3011]
HD64F3684GH@QFP64 [DX3014]
HD64F3684H@QFP64 [DX3014]
HD64F3687FP@QFP64 [DX3011]
HD64F3687GFP@QFP64 [DX3011]
HD64F3687GH@QFP64 [DX3014]
HD64F3687H@QFP64 [DX3014]
HD64F36902GFH@QFP32 [DX3001]
HD64F36902GP@SDIP32 [DX0032]
HD64F36902GTP@SOP32 [DX1034]
HD64F36912GFH@QFP32 [DX3001]

HD64F36912GP@SDIP32 [DX0032]
HD64F36912GTP@SOP32 [DX1034]
HD64F3694FP@QFP64 [DX3011]
HD64F3694FX@QFP48 [DX3008]
HD64F3694FY@QFP48 [DX3007]
HD64F3694GFP@QFP64 [DX3011]
HD64F3694GFX@QFP48 [DX3008]
HD64F3694GFY@QFP48 [DX3007]
HD64F3694GH@QFP64 [DX3014]
HD64F3694H@QFP64 [DX3014]
HD64F38002FP@TQFP64 [DX3011]
HD64F38002H@TQFP64 [DX3014]
HD64F38004FP@TQFP64 [DX3011]
HD64F38004H@TQFP64 [DX3014]
HD64F38024F@QFP80 [DX3019]
HD64F38024H@QFP80 [DX3018]
HD64F38024RF@QFP80 [DX3019]
HD64F38024RH@QFP80 [DX3018]
HD64F38024RW@QFP80 [DX3016]
HD64F38024W@QFP80 [DX3016]
HD64F38102FP@TQFP64 [DX3011]
HD64F38102H@TQFP64 [DX3014]
HD64F38104FP@TQFP64 [DX3011]
HD64F38104H@TQFP64 [DX3014]
HD64F38124D@QFP80 [DX3018]
HD64F38124H@QFP80 [DX3018]
HD64F38124W@QFP80 [DX3016]
HD64F38124WI@QFP80 [DX3016]
HD64F38324H@QFP80 [DX3018]
HD64F38324HW@QFP80 [DX3018]
HD64F38324W@QFP80 [DX3016]
HD64F38324WW@QFP80 [DX3016]
HD64F38327H@QFP80 [DX3018]
HD64F38327HW@QFP80 [DX3018]
HD64F38327W@QFP80 [DX3016]
HD64F38327WW@QFP80 [DX3016]
HD64F38424H@QFP80 [DX3018]
HD64F38424HW@QFP80 [DX3018]
HD64F38424W@QFP80 [DX3016]
HD64F38424WW@QFP80 [DX3016]
HD64F38427H@QFP80 [DX3018]
HD64F38427HW@QFP80 [DX3018]
HD64F38427W@QFP80 [DX3016]
HD64F38427WW@QFP80 [DX3016]
HD64F39012FP@QFP64 [DX3011]
HD64F39012FT@QFN48 [DX4021]
HD64F39012FX@QFP48 [DX3008]
HD64F39012FY@QFP48 [DX3007]
HD64F39012GFP@QFP64 [DX3011]
HD64F39012GFT@QFN48 [DX4021]
HD64F39012GFX@QFP48 [DX3008]
HD64F39012GFY@QFP48 [DX3007]
HD64F39014FP@QFP64 [DX3011]
HD64F39014FT@QFN48 [DX4021]
HD64F39014FX@QFP48 [DX3008]
HD64F39014FY@QFP48 [DX3007]
HD64F39014GFP@QFP64 [DX3011]
HD64F39014GFT@QFN48 [DX4021]
HD64F39014GFX@QFP48 [DX3008]
HD64F39014GFY@QFP48 [DX3007]
HD64F39022FP@QFP64 [DX3011]
HD64F39022FT@QFN48 [DX4021]
HD64F39022FX@QFP48 [DX3008]
HD64F39022FY@QFP48 [DX3007]
HD64F39022GFP@QFP64 [DX3011]
HD64F39022GFT@QFN48 [DX4021]
HD64F39022GFX@QFP48 [DX3008]
HD64F39022GFY@QFP48 [DX3007]
HD64F39024FP@QFP64 [DX3011]
HD64F39024FT@QFN48 [DX4021]
HD64F39024FX@QFP48 [DX3008]
HD64F39024FY@QFP48 [DX3007]
HD64F39024GFP@QFP64 [DX3011]
HD64F39024GFT@QFN48 [DX4021]
HD64F39024GFX@QFP48 [DX3008]
HD64F39024GFY@QFP48 [DX3007]
HD64F39802GP@SDIP32 [DX0032]
HD64F7044F28@QFP112 [DX3025]
HD64F7045F28@QFP144 [DX3035]
HD64F7046F50@QFP80 [DX3018]
HD64F7047F50@QFP100 [DX3021]
HD64F7052F40@QFP208(*) [DX3059]
HD64F7053F40@QFP208(*) [DX3059]
HD64F7054F40@QFP208(*) [DX3059]
HD64F7055F40@PQFP256(*) [DX3070]
HD64F7058F80@PQFP256(*) [DX3070]
HD64F7065AF60@QFP176 [DX3099]
HD64F7065SF60@QFP176 [DX3099]
HD64F7144F50@QFP112 [DX3025]
HD64F7144FW50@QFP112 [DX3025]
HD64F7145F50@QFP144 [DX3035]
HD64F7145FW50@QFP144 [DX3035]
R4F20102DFA [DX3011-3]
R4F20102DFB [DX3014-1]
R4F20102NFA [DX3011-3]
R4F20102NFB [DX3014-1]

R4F20102RDFA [DX3011-3]
R4F20102RNFA [DX3011-3]
R4F20103DFA [DX3011-3]
R4F20103NFA [DX3011-3]
R4F20103RDFA [DX3011-3]
R4F20103RNFA [DX3011-3]
R4F20114DFA [DX3011-3]
R4F20114NFA [DX3011-3]
R4F20114RDFA [DX3011-3]
R4F20114RNFA [DX3011-3]
R4F20115DFA [DX3011-3]
R4F20115NFA [DX3011-3]
R4F20115RDFA [DX3011-3]
R4F20115RNFA [DX3011-3]
R4F20202DFC [DX3016-1]
R4F20202NFC [DX3016-1]
R4F20202RDFC [DX3016-1]
R4F20202RNFC [DX3016-1]
R4F20203DFC [DX3016-1]
R4F20203NFC [DX3016-1]
R4F20203RDFC [DX3016-1]
R4F20203RNFC [DX3016-1]
R4F20214DFC [DX3016-1]
R4F20214NFC [DX3016-1]
R4F20214RDFC [DX3016-1]
R4F20214RNFC [DX3016-1]
R4F20215DFC [DX3016-1]
R4F20215NFC [DX3016-1]
R4F20215RDFC [DX3016-1]
R4F20215RNFC [DX3016-1]
R4F20222DFC [DX3016-1]
R4F20222NFC [DX3016-1]
R4F20222RDFC [DX3016-1]
R4F20222RNFC [DX3016-1]
R4F20223DFC [DX3016-1]
R4F20223NFC [DX3016-1]
R4F20223RDFC [DX3016-1]
R4F20223RNFC [DX3016-1]
R4F20234DFC [DX3016-1]
R4F20234NFC [DX3016-1]
R4F20234RDFC [DX3016-1]
R4F20234RNFC [DX3016-1]
R4F20235DFC [DX3016-1]
R4F20235NFC [DX3016-1]
R4F20235RDFC [DX3016-1]
R4F20235RNFC [DX3016-1]
R4F20322RDFE [DX3021-2]
R4F20323RDFE [DX3021-2]
R4F20102RDFB [DX3014-1]
R4F20102RNFB [DX3014-1]
R4F20103DFB [DX3014-1]
R4F20103NFB [DX3014-1]
R4F20103RDFB [DX3014-1]
R4F20103RNFB [DX3014-1]
R4F20114DFB [DX3014-1]
R4F20114NFB [DX3014-1]
R4F20114RDFB [DX3014-1]
R4F20114RNFB [DX3014-1]
R4F20115DFB [DX3014-1]
R4F20115NFB [DX3014-1]
R4F20115RDFB [DX3014-1]
R4F20115RNFB [DX3014-1]
R4F20202DFD [DX3018-1]
R4F20202NFD [DX3018-1]
R4F20202RDFD [DX3018-1]
R4F20202RNFD [DX3018-1]
R4F20203DFD [DX3018-1]
R4F20203NFD [DX3018-1]
R4F20203RDFD [DX3018-1]
R4F20203RNFD [DX3018-1]
R4F20214DFD [DX3018-1]
R4F20214NFD [DX3018-1]
R4F20214RDFD [DX3018-1]
R4F20214RNFD [DX3018-1]
R4F20215DFD [DX3018-1]
R4F20215NFD [DX3018-1]
R4F20215RDFD [DX3018-1]
R4F20215RNFD [DX3018-1]
R4F20222DFD [DX3018-1]
R4F20222NFD [DX3018-1]
R4F20222RDFD [DX3018-1]
R4F20222RNFD [DX3018-1]
R4F20223DFD [DX3018-1]
R4F20223NFD [DX3018-1]
R4F20223RDFD [DX3018-1]
R4F20223RNFD [DX3018-1]
R4F20234DFD [DX3018-1]
R4F20234NFD [DX3018-1]
R4F20234RDFD [DX3018-1]
R4F20234RNFD [DX3018-1]
R4F20235DFD [DX3018-1]
R4F20235NFD [DX3018-1]
R4F20235RDFD [DX3018-1]
R4F20235RNFD [DX3018-1]
R4F20322RNFE [DX3021-2]
R4F20323RNFE [DX3021-2]

R4F20334RDFE [DX3021-2]
R4F20335RDFE [DX3021-2]
R4F2112BG25@FBGA176 [DX5163]
R4F2112RTE25@TQFP144 [DX3034]
R4F2112RVTE25@TQFP144 [DX3034]
R4F2112VBG25@FBGA176 [DX5163]
R4F2113NFT@QFP144 [DX3034]
R4F2116RBG20@FBGA176 [DX5163]
R4F2116RVBG20@FBGA176 [DX5163]
R4F2116TE20@QFP144 [DX3034]
R4F2116VTE20@QFP144 [DX3034]
R4F2117RBG20@FBGA176 [DX5163]
R4F2117RVBG20@FBGA176 [DX5163]
R4F2117TE20@TQFP144 [DX3034]
R4F2117VTE20@TQFP144 [DX3034]
R4F24245DFPV [DX3027]
R4F24245DVFPV [DX3027]
R4F24245NFPV [DX3027]
R4F24245NVFPV [DX3027]
R4F24248DFPV [DX3027]
R4F24248DVFPV [DX3027]
R4F24248NFPV [DX3027]
R4F24248NVFPV [DX3027]
R4F24249DFPV [DX3027]
R4F24249DVFPV [DX3027]
R4F24249NFPV [DX3027]
R4F24249NVFPV [DX3027]
R4F24255DFPU [DX3027]
R4F24255DVFPU [DX3027]
R4F24255NFPU [DX3027]
R4F24255NVFPU [DX3027]
R4F24256DFPU [DX3027]
R4F24256DVFPU [DX3027]
R4F24256NFPU [DX3027]
R4F24256NVFPU [DX3027]
R4F24258DFPU [DX3027]
R4F24258DVFPU [DX3027]
R4F24258NFPU [DX3027]
R4F24258NVFPU [DX3027]
R4F24259DFPU [DX3027]
R4F24259DVFPU [DX3027]
R4F24259NFPU [DX3027]
R4F24259NVFPU [DX3027]
R4F24265DVFQV [DX3051]
R4F24265NFQV [DX3051]
R4F24265NVRFQV [DX3051]
R4F24268DVFQV [DX3051]
R4F24268NFQV [DX3051]
R4F20334RNFE [DX3021-2]
R4F20335RNFE [DX3021-2]
R4F2112RBG25@FBGA176 [DX5163]
R4F2112RVBG25@FBGA176 [DX5163]
R4F2112TE25@TQFP144 [DX3034]
R4F2112VTE25@TQFP144 [DX3034]
R4F2116BG20@FBGA176 [DX5163]
R4F2116RTE20@QFP144 [DX3034]
R4F2116RVTE20@QFP144 [DX3034]
R4F2116VBG20@FBGA176 [DX5163]
R4F2117BG20@FBGA176 [DX5163]
R4F2117RTE20@TQFP144 [DX3034]
R4F2117RVTE20@TQFP144 [DX3034]
R4F2117VBG20@FBGA176 [DX5163]
R4F24245DFAU [DX3028]
R4F24245DVFAU [DX3028]
R4F24245NFAU [DX3028]
R4F24245NVFAU [DX3028]
R4F24248DFAU [DX3028]
R4F24248DVFAU [DX3028]
R4F24248NFAU [DX3028]
R4F24248NVFAU [DX3028]
R4F24249DFAU [DX3028]
R4F24249DVFAU [DX3028]
R4F24249NFAU [DX3028]
R4F24249NVFAU [DX3028]
R4F24255DFAU [DX3028]
R4F24255DVFAU [DX3028]
R4F24255NFAU [DX3028]
R4F24255NVFAU [DX3028]
R4F24256DFAU [DX3028]
R4F24256DVFAU [DX3028]
R4F24256NFAU [DX3028]
R4F24256NVFAU [DX3028]
R4F24258DFAU [DX3028]
R4F24258DVFAU [DX3028]
R4F24258NFAU [DX3028]
R4F24258NVFAU [DX3028]
R4F24259DFAU [DX3028]
R4F24259DVFAU [DX3028]
R4F24259NFAU [DX3028]
R4F24259NVFAU [DX3028]
R4F24265DFQV [DX3051]
R4F24265DVRFQV [DX3051]
R4F24265NVFQV [DX3051]
R4F24268DFQV [DX3051]
R4F24268DVRFQV [DX3051]
R4F24268NVFQV [DX3051]

R4F24268NVRFQV [DX3051]
R4F24269DFQV [DX3051]
R4F24269DVFQV [DX3051]
R4F24269DVRFQV [DX3051]
R4F24269NFQV [DX3051]
R4F24269NVFQV [DX3051]
R4F24269NVRFQV [DX3051]
R4F24275DFQU [DX3051]
R4F24275DVFQU [DX3051]
R4F24275DVRFQU [DX3051]
R4F24275NFQU [DX3051]
R4F24275NVFQU [DX3051]
R4F24275NVRFQU [DX3051]
R4F24276DFQU [DX3051]
R4F24276DVFQU [DX3051]
R4F24276DVRFQU [DX3051]
R4F24276NFQU [DX3051]
R4F24276NVFQU [DX3051]
R4F24276NVRFQU [DX3051]
R4F24278DFQU [DX3051]
R4F24278DVFQU [DX3051]
R4F24278DVRFQU [DX3051]
R4F24278NFQU [DX3051]
R4F24278NVFQU [DX3051]
R4F24278NVRFQU [DX3051]
R4F24279DFQU [DX3051]
R4F24279DVFQU [DX3051]
R4F24279DVRFQU [DX3051]
R4F24279NFQU [DX3051]
R4F24279NVFQU [DX3051]
R4F24279NVRFQU [DX3051]
R4F24545DVFAU [DX3028]
R4F24545DVFPV [DX3027]
R4F24545NVFAU [DX3028]
R4F24545NVFPV [DX3027]
R4F24548DVFAU [DX3028]
R4F24548DVFPV [DX3027]
R4F24548NVFAU [DX3028]
R4F24548NVFPV [DX3027]
R4F24549DVFAU [DX3028]
R4F24549DVFPV [DX3027]
R4F24549NVFAU [DX3028]
R4F24549NVFPV [DX3027]
R4F24565DVFQV [DX3051]
R4F24565DVRFQV [DX3051]
R4F24565NVFQV [DX3051]
R4F24565NVRFQV [DX3051]
R4F24568DVFQV [DX3051]
R4F24568DVRFQV [DX3051]
R4F24568NVFQV [DX3051]
R4F24568NVRFQV [DX3051]
R4F24569DVFQV [DX3051]
R4F24569DVRFQV [DX3051]
R4F24569NVFQV [DX3051]
R4F24569NVRFQV [DX3051]
R4F2463VTE34DV@TQFP144 [DX3034]
R4F2463VTE34V@TQFP144 [DX3034]
R5F61523FP@QFP100 [DX3043]
R5F61524FP@QFP100 [DX3043]
R5F61525FP@QFP100 [DX3043]
R5F61527FP@QFP100 [DX3043]
R5F61632FPV@QFP120 [DX3027]
R5F61632LFPV@QFP120 [DX3027]
R5F61634FPV@QFP120 [DX3027]
R5F61634LFPV@QFP120 [DX3027]
R5F61638FPV@QFP120 [DX3027]
R5F61638LFPV@QFP120 [DX3027]
R5F61641FPV@QFP144 [DX3035]
R5F61641LFPV@QFP144 [DX3035]
R5F61642AFPV@QFP144 [DX3035]
R5F61642FPV@QFP144 [DX3035]
R5F61642LFPV@QFP144 [DX3035]
R5F61643FPV@QFP144 [DX3035]
R5F61643LFPV@QFP144 [DX3035]
R5F61644AFPV@QFP144 [DX3035]
R5F61644FPV@QFP144 [DX3035]
R5F61644LFPV@QFP144 [DX3035]
R5F61645FPV@QFP144 [DX3035]
R5F61645LFPV@QFP144 [DX3035]
R5F61648AFPV@QFP144 [DX3035]
R5F61648FPV@QFP144 [DX3035]
R5F61648LFPV@QFP144 [DX3035]
R5F61652FPV@QFP120 [DX3027]
R5F61652MFPV@QFP120 [DX3027]
R5F61653MFPV@QFP120 [DX3027]
R5F61653RFPV@QFP120 [DX3027]
R5F61654MFPV@QFP120 [DX3027]
R5F61654RFPV@QFP120 [DX3027]
R5F61655FPV@QFP120 [DX3027]
R5F61655MFPV@QFP120 [DX3027]
R5F61658MFPV@QFP120 [DX3027]
R5F61658RFPV@QFP120 [DX3027]
R5F61663MFPV@QFP144 [DX3035]
R5F61663RFPV@QFP144 [DX3035]
R5F61664MFPV@QFP144 [DX3035]
R5F61664RFPV@QFP144 [DX3035]

R5F61668MFPV@QFP144 [DX3035]
R5F61668RFPV@QFP144 [DX3035]
R5F61725FPV@QFP100 [DX3043]
R5F61725SFPV@QFP100 [DX3043]
R5F61726SFPV@QFP100 [DX3043]
R5F61727SFPV@QFP100 [DX3043]
R5F70834AD80BGV [DX5058]
R5F70834AD80FTV@QFP100 [DX3043]
R5F70834AN80BGV [DX5058]
R5F70834AN80FTV@QFP100 [DX3043]
R5F70835AD80FTV@QFP100 [DX3043]
R5F70835AN80FTV@QFP100 [DX3043]
R5F70844AD80FPV@QFP112 [DX3026]
R5F70844AN80FPV@QFP112 [DX3026]
R5F70845AD80FPV@QFP112 [DX3026]
R5F70845AN80FPV@QFP112 [DX3026]
R5F70854AD80FPV@TQFP144 [DX3035]
R5F70854AN80FPV@TQFP144 [DX3035]
R5F70855AD80FPV@TQFP144 [DX3035]
R5F70855AN80FPV@TQFP144 [DX3035]
R5F70865AD80FPV@QFP176 [DX3080]
R5F70865AN80FPV@QFP176 [DX3080]
R5F71242FPV@QFP48(serial) [DX3008]
R5F71243FPV@QFP48(serial) [DX3008]
R5F71252FAV@QFP64(serial) [DX3014]
R5F71252FPV@QFP64(serial) [DX3011]
R5F71253FAV@QFP64(serial) [DX3014]
R5F71253FPV@QFP64(serial) [DX3011]
R5F71374AD80FPV@QFP100 [DX3043]
R5F71374AN80FPV@QFP100 [DX3043]
R5F71424AK64FPV@QFP100 [DX3043]
R5F71424BJ80FPV@QFP100 [DX3043]
R5F71426AK64FPV@QFP100 [DX3043]
R5F71426BD80FPV@QFP100 [DX3043]
R5F71426BJ80FPV@QFP100 [DX3043]
R5F71464FPV@QFP80 [DX3017]
R5F71464FPV@QFP80(serial) [DX3017]
R5F71474AK64FPV@QFP100 [DX3043]
R5F71474BD80FPV@QFP100 [DX3043]
R5F71474BJ80FPV [DX3043]
R5F71475AK64FPV [DX3043]
R5F71475BD80FPV [DX3043]
R5F71475BJ80FPV [DX3043]
R5F71476AK64FPV [DX3043]
R5F71476BD80FPV [DX3043]
R5F71476BJ80FPV [DX3043]
R5F71494FPV@QFP100 [DX3021]
R5F72114FPV@QFP144 [DX3035]
R5F72115FPV@QFP144 [DX3035]
R5F72145ADFA@QFP176 [DX3089]
R5F72145ADFP@QFP176 [DX3111]
R5F72145BDFA@QFP176 [DX3089]
R5F72145BDFP@QFP176 [DX3111]
R5F72145GDFA@QFP176 [DX3089]
R5F72145GDFP@QFP176 [DX3111]
R5F72145HDFA@QFP176 [DX3089]
R5F72145HDFP@QFP176 [DX3111]
R5F72146ADFA@QFP176 [DX3089]
R5F72146ADFP@QFP176 [DX3111]
R5F72146BDFA@QFP176 [DX3089]
R5F72146BDFP@QFP176 [DX3111]
R5F72146GDFA@QFP176 [DX3089]
R5F72146GDFP@QFP176 [DX3111]
R5F72146HDFA@QFP176 [DX3089]
R5F72146HDFP@QFP176 [DX3111]
R5F72147ADFA@QFP176 [DX3089]
R5F72147ADFP@QFP176 [DX3111]
R5F72147BDFA@QFP176 [DX3089]
R5F72147BDFP@QFP176 [DX3111]
R5F72147GDFA@QFP176 [DX3089]
R5F72147GDFP@QFP176 [DX3111]
R5F72147HDFA@QFP176 [DX3089]
R5F72147HDFP@QFP176 [DX3111]
R5F72165ADFA@QFP176 [DX3089]
R5F72165ADFP@QFP176 [DX3111]
R5F72165BDFA@QFP176 [DX3089]
R5F72165BDFP@QFP176 [DX3111]
R5F72165GDFA@QFP176 [DX3089]
R5F72165GDFP@QFP176 [DX3111]
R5F72165HDFA@QFP176 [DX3089]
R5F72165HDFP@QFP176 [DX3111]
R5F72166ADFA@QFP176 [DX3089]
R5F72166ADFP@QFP176 [DX3111]
R5F72166BDFA@QFP176 [DX3089]
R5F72166BDFP@QFP176 [DX3111]
R5F72166GDFA@QFP176 [DX3089]
R5F72166GDFP@QFP176 [DX3111]
R5F72166HDFA@QFP176 [DX3089]
R5F72166HDFP@QFP176 [DX3111]

R5F72167ADFA@QFP176 [DX3089]
R5F72167BDFA@QFP176 [DX3089]
R5F72167GDFA@QFP176 [DX3089]
R5F72167HDFA@QFP176 [DX3089]
R5F72865DFP [DX3114]
R5F72866DFP [DX3114]
R5F72867DFP [DX3114]
R5F72167ADFP@QFP176 [DX3111]
R5F72167BDFP@QFP176 [DX3111]
R5F72167GDFP@QFP176 [DX3111]
R5F72167HDFP@QFP176 [DX3111]
R5F72865NFP [DX3114]
R5F72866NFP [DX3114]
R5F72867NFP [DX3114]

HITRENDTECH

MICROCONTROLLER

ATT7025@QFP64 [DX3011]

HODGEN

MICROCONTROLLER

uPD78F0524AGB@LQFP52 [DX3010]
uPD78F0525AGB@LQFP52 [DX3010]
uPD78F0524GB@LQFP52 [DX3010]
uPD78F0525GB@LQFP52 [DX3010]

HOLTEK

E(E)PROM/FRAM/NVRAM

HT24C01 [DX0001]
HT24C02 [DX0001]
HT24C04 [DX0001]
HT24C08 [DX0001]
HT24LC01 [DX0001]
HT24LC01@TSSOP8 [DX1059]
HT24LC02@SOIC8 [DX1045]
HT24LC04 [DX0001]
HT24LC08 [DX0001]
HT24LC16 [DX0001]
HT24LC32 [DX0001]
HT24LC64 [DX0001]
HT25LC512@SOIC8 [DX1045]
HT27C010@PLCC32 [DX2032]
HT27C020 [DX0001]
HT27C020@SOP32 [DX1034]
HT27C040@PLCC32 [DX2032]
HT27C4096 [DX0001]
HT27C512 [DX0001]
HT27C512-A@PLCC32 [DX2032]
HT24C01@SOIC8 [DX1045]
HT24C02@SOIC8 [DX1045]
HT24C04@SOIC8 [DX1045]
HT24C16 [DX0001]
HT24LC01@SOIC8 [DX1045]
HT24LC02 [DX0001]
HT24LC02@TSSOP8 [DX1059]
HT24LC04@SOIC8 [DX1045]
HT24LC08@SOIC8 [DX1045]
HT24LC16@SOIC8 [DX1045]
HT24LC32@SOIC8 [DX1045]
HT24LC64@SOIC8 [DX1045]
HT27C010 [DX0001]
HT27C010@SOP32 [DX1034]
HT27C020@PLCC32 [DX2032]
HT27C040 [DX0001]
HT27C040@SOP32 [DX1034]
HT27C4096@PLCC44 [DX2044]
HT27C512@SOP28 [DX1033]
HT27C512-B@PLCC32 [DX2032]

HT27LC010 [DX0001]
HT27LC010@PLCC32 [DX2032]
HT27LC010@SOP32 [DX1034]
HT27LC010@TSOP32 [DX1002]
HT27LC020 [DX0001]
HT27LC020@PLCC32 [DX2032]
HT27LC020@SOP32 [DX1034]
HT27LC020@TSOP32 [DX1002]
HT27LC040 [DX0001]
HT27LC040@PLCC32 [DX2032]
HT27LC040@SOP32 [DX1034]
HT27LC040@TSOP32 [DX1002]
HT27LC4096 [DX0001]
HT27LC4096@PLCC44 [DX2044]
HT27LC512 [DX0001]
HT27LC512@SOP28 [DX1033]
HT27LC512@TSOP28 [DX1024]
HT27LC512-A@PLCC32 [DX2032]
HT27LC512-B@PLCC32 [DX2032]
HT93C46(16bit) [DX0001]
HT93C46(16bit)@SOP8-A [DX1045]
HT93C46(16bit)@SOP8-B [DX1045]
HT93C46(16bit)@TSSOP8 [DX1059]
HT93C56(16bit) [DX0001]
HT93C56(16bit)@SOP8-A [DX1045]
HT93C56(16bit)@SOP8-B [DX1045]
HT93C56(16bit)@TSSOP8 [DX1059]
HT93C66(16bit) [DX0001]
HT93C66(16bit)@SOP8-A [DX1045]
HT93C66(16bit)@SOP8-B [DX1045]
HT93C66(16bit)@TSSOP8 [DX1059]
HT93LC46A(08bit) [DX0001]
HT93LC46A(08bit)@SOP8-A [DX1045]
HT93LC46A(08bit)@SOP8-B [DX1045]
HT93LC46A(08bit)@TSSOP8 [DX1059]
HT93LC46A(16bit) [DX0001]
HT93LC46A(16bit)@SOP8-A [DX1045]
HT93LC46A(16bit)@SOP8-B [DX1045]
HT93LC46A(16bit)@TSSOP8 [DX1059]
HT93LC46B(08bit) [DX0001]
HT93LC46B(08bit)@SOP8-A [DX1045]
HT93LC46B(08bit)@SOP8-B [DX1045]
HT93LC46B(08bit)@TSSOP8 [DX1059]
HT93LC46B(16bit) [DX0001]
HT93LC46B(16bit)@SOP8-A [DX1045]
HT93LC46B(16bit)@SOP8-B [DX1045]
HT93LC46B(16bit)@TSSOP8 [DX1059]
HT93LC56A(08bit) [DX0001]
HT93LC56A(08bit)@SOP8-A [DX1045]
HT93LC56A(08bit)@SOP8-B [DX1045]
HT93LC56A(08bit)@TSSOP8 [DX1059]
HT93LC56A(16bit) [DX0001]
HT93LC56A(16bit)@SOP8-A [DX1045]
HT93LC56A(16bit)@SOP8-B [DX1045]
HT93LC56A(16bit)@TSSOP8 [DX1059]
HT93LC56B(08bit) [DX0001]
HT93LC56B(08bit)@SOP8-A [DX1045]
HT93LC56B(08bit)@SOP8-B [DX1045]
HT93LC56B(08bit)@TSSOP8 [DX1059]
HT93LC56B(16bit) [DX0001]
HT93LC56B(16bit)@SOP8-A [DX1045]
HT93LC56B(16bit)@SOP8-B [DX1045]
HT93LC56B(16bit)@TSSOP8 [DX1059]
HT93LC66A(08bit) [DX0001]
HT93LC66A(08bit)@SOP8-A [DX1045]
HT93LC66A(08bit)@SOP8-B [DX1045]
HT93LC66A(08bit)@TSSOP8 [DX1059]
HT93LC66A(16bit) [DX0001]
HT93LC66A(16bit)@SOP8-A [DX1045]
HT93LC66A(16bit)@SOP8-B [DX1045]
HT93LC66A(16bit)@TSSOP8 [DX1059]
HT93LC66B(08bit) [DX0001]
HT93LC66B(08bit)@SOP8-A [DX1045]
HT93LC66B(08bit)@SOP8-B [DX1045]
HT93LC66B(08bit)@TSSOP8 [DX1059]
HT93LC66B(16bit) [DX0001]
HT93LC66B(16bit)@SOP8-A [DX1045]
HT93LC66B(16bit)@SOP8-B [DX1045]
HT93LC66B(16bit)@TSSOP8 [DX1059]
HT93LC76(08bit) [DX0001]
HT93LC76(08bit)@SOP8-A [DX1045]
HT93LC76(08bit)@SOP8-B [DX1045]
HT93LC76(08bit)@TSSOP8 [DX1059]
HT93LC76(16bit) [DX0001]
HT93LC76(16bit)@SOP8-A [DX1045]
HT93LC76(16bit)@SOP8-B [DX1045]
HT93LC76(16bit)@TSSOP8 [DX1059]
HT93LC86(08bit) [DX0001]
HT93LC86(08bit)@SOP8-A [DX1045]
HT93LC86(08bit)@SOP8-B [DX1045]
HT93LC86(08bit)@TSSOP8 [DX1059]
HT93LC86(16bit) [DX0001]
HT93LC86(16bit)@SOP8-A [DX1045]
HT93LC86(16bit)@SOP8-B [DX1045]
HT93LC86(16bit)@TSSOP8 [DX1059]

MICROCONTROLLER

HT45R38@QFP52 [DX3048]
HT46R22@SOP24 [DX1033]
HT46R23(dip28) [DX0001]
HT46R23@SOP28 [DX1033]
HT46R232@SOP28 [DX1033]
HT46R24 [DX0001]
HT46R24@SSOP48 [DX1028]
HT46R46(dip18) [DX0001]
HT46R46@SOP18 [DX1033]
HT46R46@SSOP20 [DX1025]
HT46R46-H@SOP18 [DX1033]
HT46R47(dip20) [DX0001]
HT46R47@SOP20 [DX1033]
HT46R47-H [DX0001]
HT46R48(dip20) [DX0001]
HT46R48@SOP20 [DX1033]
HT46R48@SSOP24 [DX1025]
HT46R51A@SOP20 [DX1033]
HT46R52A(dip18) [DX0001]
HT46R52A@SSOP20 [DX1025]
HT46R53A@SOP28 [DX1033]
HT46R54A@SOP28 [DX1033]
HT46R63@PQFP100 [DX3023]
HT46R64@PQFP100 [DX3023]
HT46R65@PQFP100 [DX3023]
HT46R652@PQFP100 [DX3023]
HT46R74D@SSOP56 [DX1054]
HT46RB50@SOP28 [DX1033]
HT46RB70 [DX0001]
HT46RB70@SSOP48 [DX1028]
HT46RU22@SOP24 [DX1033]
HT46RU25@SSOP48 [DX1028]
HT47R10A@QFP44 [DX3002]
HT48R05A [DX0001]
HT48R05A@SOP18 [DX1033]
HT48R06A@SOP16 [DX1016]
HT48R07A [DX0001]
HT48R07A@SSOP24 [DX1025]
HT48R08A@SOP16 [DX1000]
HT48R09A [DX0001]
HT48R09A@SSOP24 [DX1025]
HT48R10A@SOP24 [DX1033]
HT48R30A(dip28) [DX0001]
HT48R30A@SOP28 [DX1033]
HT46R22 [DX0001]
HT46R23(dip24) [DX0001]
HT46R23@SOP24 [DX1033]
HT46R232 [DX0001]
HT46R232@SSOP48 [DX1028]
HT46R24@SOP28 [DX1033]
HT46R342@QFP44 [DX3002]
HT46R46(dip20) [DX0001]
HT46R46@SOP20 [DX1033]
HT46R46-H [DX0001]
HT46R47(dip18) [DX0001]
HT46R47@SOP18 [DX1033]
HT46R47@SSOP20 [DX1025]
HT46R47-H@SOP18 [DX1033]
HT46R48(dip24) [DX0001]
HT46R48@SOP24 [DX1033]
HT46R51A(dip18) [DX0001]
HT46R51A@SSOP20 [DX1025]
HT46R52A@SOP20 [DX1033]
HT46R53A(dip28) [DX0001]
HT46R54A(dip28) [DX0001]
HT46R62@SSOP56 [DX1054]
HT46R63@SSOP56 [DX1054]
HT46R64@SSOP56 [DX1054]
HT46R65@SSOP56 [DX1054]
HT46R71D@SSOP48 [DX1028]
HT46RB50 [DX0001]
HT46RB50@SSOP48 [DX1028]
HT46RB70@SOP28 [DX1033]
HT46RU22 [DX0001]
HT46RU22@SSOP24 [DX1025]
HT46RU25@SSOP56 [DX1054]
HT47R20A@QFP64 [DX3049]
HT48R05A@SOP16 [DX1000]
HT48R06A [DX0001]
HT48R06A@SOP18 [DX1033]
HT48R07A@SOP24 [DX1033]
HT48R08A [DX0001]
HT48R08A@SOP18 [DX1033]
HT48R09A@SOP24 [DX1033]
HT48R10A [DX0001]
HT48R30A(dip24) [DX0001]
HT48R30A@SOP24 [DX1033]
HT48R502A@QFP64

HT48R502A@SSOP48 [DX1028]
HT48R50A@SOP28 [DX1028]
HT48R52A@QFP44 [DX3002]
HT48R54A@QFP52 [DX3048]
HT48R70A@SSOP48 [DX1028]
HT48RA0-1@SOP24 [DX1033]
HT48RA0-2@SOP20 [DX1033]
HT48RA0-3 [DX0001]
HT48RA1@SOP28 [DX1033]
HT48RA3 [DX0001]
HT48RA3@SSOP28 [DX1025]
HT48RA5@SOP28 [DX1033]
HT48RB50 [DX0001]
HT48RB50@SSOP48 [DX1028]
HT48RB8@SSOP48 [DX1028]
HT48RU80@SSOP48 [DX1028]
HT49R30A@SSOP48 [DX1028]
HT49R50A@SSOP48 [DX1028]
HT49RU80@QFP100 [DX3023]
HT49RV5@SSOP56 [DX1054]
HT82A523R@LQFP32 [DX3001]
HT82A523R@LQFP64 [DX30UN]
HT82A821R@SOP24 [DX1033]
HT82A822R@SSOP48 [DX1028]
HT82A832R@SSOP48 [DX1028]
HT82J97E@SOP28 [DX1033]
HT82K68E@SOP20 [DX1033]
HT82K68E@SSOP48 [DX1028]
HT82K95A@QFN32 [DX4015]
HT82K95A@SSOP48 [DX1028]
HT82K95E@SOP20 [DX1033]
HT82K95E@SSOP48 [DX1028]
HT82K96A@SSOP48 [DX1028]
HT82K96E(dip40) [DX0001]
HT82K96E@SOP28 [DX1033]
HT82M99E(dip18) [DX0001]
HT82M99E@SOP18 [DX1033]
HT82M9AE@SOP20 [DX1033]
HT82M9AE@SSOP20 [DX1025]
HT82M9BE@SOP24 [DX1033]
HT82M9BE@SSOP24 [DX1025]
HT95A100@SOP28 [DX1033]
HT95A200@SSOP48 [DX1028]
HT95A300@SSOP48 [DX1028]
HT95A400@PQFP64 [DX3015]
HT95L000@SSOP56 [DX1054]
HT95L100@PQFP64 [DX3049]
HT95L200@QFP100 [DX3023]
HT48R50A [DX0001]
HT48R50A@SSOP48 [DX1028]
HT48R54A@QFP44 [DX3002]
HT48R70A@PQFP64 [DX3049]
HT48RA0-1 [DX0001]
HT48RA0-2 [DX0001]
HT48RA0-2@SSOP20 [DX1025]
HT48RA0-3@SOP20 [DX1033]
HT48RA1@SSOP28 [DX1026]
HT48RA3@SOP28 [DX1033]
HT48RA5 [DX0001]
HT48RA5@SSOP28 [DX1025]
HT48RB50@SOP28 [DX1033]
HT48RB8@SOP28 [DX1033]
HT48RU80@QFP64 [DX3015]
HT49R10A@QFP44 [DX3002]
HT49R50A@QFP100 [DX3023]
HT49R70A@QFP100 [DX3023]
HT49RV3@QFP52 [DX3048]
HT49RV7@PQFP100 [DX3023]
HT82A523R@LQFP52 [DX3048]
HT82A523R@SSOP48 [DX1028]
HT82A821R@SSOP24 [DX1025]
HT82A832R@QFP48 [DX3007]
HT82J97E@SOP20 [DX1033]
HT82K68E [DX0001]
HT82K68E@SOP28 [DX1033]
HT82K94E@SSOP48 [DX1028]
HT82K95A@SOP28 [DX1033]
HT82K95E@QFN32 [DX4015]
HT82K95E@SOP28 [DX1033]
HT82K96A@SOP28 [DX1033]
HT82K96E(dip20) [DX0001]
HT82K96E@SOP20 [DX1033]
HT82K96E@SSOP48 [DX1028]
HT82M99E(dip20) [DX0001]
HT82M99E@SOP20 [DX1033]
HT82M9AE@SOP24 [DX1033]
HT82M9AE@SSOP24 [DX1025]
HT82M9BE@SOP28 [DX1033]
HT82M9BE@SSOP28 [DX1026]
HT95A10P@SOP28 [DX1033]
HT95A20P@SSOP48 [DX1028]
HT95A30P@SSOP48 [DX1028]
HT95A40P@PQFP64 [DX3015]
HT95L00P@SSOP56 [DX1054]
HT95L10P@PQFP64 [DX3049]
HT95L20P@QFP100 [DX3023]

HT95L300@QFP100 [DX3023]
HT95L30P@QFP100 [DX3023]

HONEYWELL

E(E)PROM/FRAM/NVRAM

HXNV0100@QFP64 [DX3011]

HONGKONG

E(E)PROM/FRAM/NVRAM

HK1215 [DX0001]
HK1225 [DX0001]
HK1235 [DX0001]
HK1245
HK1255
HK1265
HK1275 [DX0001]
HK1285 [DX0001]
HK1295 [DX0001]
HK12A5 [DX0001]
HK12B5 [DX0001]
OKS1225 [DX0001]
OKS1235 [DX0001]
OKS1245
OKS1255
OKS1265
OKS1275 [DX0001]
OKS1285 [DX0001]
OKS1295 [DX0001]
OKS12A5 [DX0001]
OKS12B5 [DX0001]

HOPEFIND

E(E)PROM/FRAM/NVRAM

HM24LC01 [DX0001]
HM24LC01@SOP8 [DX1045]
HM24LC01@TSSOP8 [DX1059]
HM24LC02 [DX0001]
HM24LC02@SOP8 [DX1045]
HM24LC02@TSSOP8 [DX1059]
HM24LC04 [DX0001]
HM24LC04@SOP8 [DX1045]
HM24LC04@TSSOP8 [DX1059]
HM24LC08 [DX0001]
HM24LC08@SOP8 [DX1045]
HM24LC08@TSSOP8 [DX1059]
HM24LC16 [DX0001]
HM24LC16@SOP8 [DX1045]
HM24LC16@TSSOP8 [DX1059]

HUAJIE Technology

E(E)PROM/FRAM/NVRAM

K24C02 [DX0001]
K24C02@SOP8 [DX1045]
K24C02@TSSOP8 [DX1059]
K24C02C [DX0001]
K24C02C@SOP8 [DX1045]
K24C02C@TSSOP8 [DX1059]
K24C04 [DX0001]
K24C04@SOP8 [DX1045]

K24C04@TSSOP8 [DX1059]
K24C04C [DX0001]
K24C04C@SOP8 [DX1045]
K24C04C@TSSOP8 [DX1059]
K24C08 [DX0001]
K24C08@SOP8 [DX1045]
K24C08@TSSOP8 [DX1059]
K24C08C [DX0001]
K24C08C@SOP8 [DX1045]
K24C08C@TSSOP8 [DX1059]
K24C16 [DX0001]
K24C16@SOP8 [DX1045]
K24C16@TSSOP8 [DX1059]
K24C16C [DX0001]
K24C16C@SOP8 [DX1045]
K24C16C@TSSOP8 [DX1059]
K34C02 [DX0001]
K34C02@SOP8 [DX1045]
K34C02@TSSOP8 [DX1059]

HUAWEI

MICROCONTROLLER

AT89C51ED2@PLCC44 [DX2044]
SD5000@LQFP176 [DX3058]
SD5000RQ1@LQFP176 [DX3058]

HYNITRON

MICROCONTROLLER

CSM212 [DX1033-8]
CSM212-Q [DX4008]
CSM212-S [DX1016-4]
CSM216 [DX1033-8]
CSM216-Q [DX4011-1]
CSM216-S [DX1026-1]
CSM224 [DX1033-8]
CSM224-Q [DX4033-1]
CSM224-S [DX1026-1]

HYNIX

E(E)PROM/FRAM/NVRAM

H26M11002AAR@FBGA169 [DX5113-1]
H26M21001DAR(20M)@FBGA169 [DX5113-1]
H26M21001DAR(2G)@FBGA169 [DX5113-1]
H26M21001ECR(20M)@FBGA153 [DX5104-1]
H26M21001ECR(2G)@FBGA153 [DX5104-1]
H26M31001FPR(20M)@FBGA153 [DX5104-1]
H26M31001FPR(2G)@FBGA153 [DX5104-1]
H26M54001DQR(20M)@FBGA169 [DX5113-1]
H26M54001DQR(2G)@FBGA169 [DX5113-1]
H26M64002DQRS(20M)@BGA169 [DX5113-1]
H26M64002DQRS(2G)@BGA169 [DX5113-1]
H27S1G8F2BFR@FBGA63 [DX5046]
H27U1G8F2BFR@FBGA63 [DX5046]
H27U1G8F2BTR@TSOP48 [DX1004-3]
H27U1G8F2CTR@TSOP48 [DX1004-1]

H27U2G8F2CTR@TSIP48 [DX1004-3]
H27U4G8F2DTR@TSOP48 [DX1004-3]
H27U4G8T2BTR@TSOP48 [DX1004-3]
H27U518S2CTP@TSOP48 [DX1004]
H27U518S2CTR@TSOP48 [DX1004]
H27U8G8G5DTR@TSOP48 [DX1004-1]
H27U8G8T2B@TSOP48 [DX1004-1]
H27UAG8T2ATR@TSOP48 [DX1004]
H27UAG8T2BTR@TSOP48 [DX1004-3]
H27UAG8T2MTR@TSOP48 [DX1004-1]
H27UBG8T2ATR@TSOP48 [DX1004-3]
H27UBG8U5MTR@TSOP48 [DX1004-1]
H8ACS0CE0ABR@FBGA107 [DX5028]
H8ACS0CF0ACR56M@FBGA137 [DX5011]
H8ACS0CF0MMR@FBGA130 [DX5140]
H8ACS0EH0ACR@FBGA137 [DX5011]
H8ACS0EH0BCR@FBGA137 [DX5011]
H8ACS0EJ0MCP@FBGA137 [DX5011]
H8ACS0PE0MBR@FBGA107 [DX5028]
H8ACS0PG0MBP@FBGA107 [DX5028]
H8ACS0PH0ACR@FBGA137 [DX5011-1]
H8ACS0PH0MCP@FBGA137 [DX5011-1]
H8ACS0PL0ACR@FBGA137 [DX5011-1]
H8ACS0PL0MCR@FBGA137 [DX5011]
H8ACS0QJ0MCR@FBGA137 [DX5011-1]
H8ACS0SI0MBR@FBGA107 [DX5028]
H8ACS0SJ0MCR@FBGA137 [DX5011]
H8ACU0CE0BBR36M@FBGA107 [DX5028]
H8ACU0CE0DAR@FBGA149 [DX5030]
H8ACU0CF0BCR@FBGA137 [DX5011]
H8ACU0CL0ACR@FBGA137 [DX5011]
H8ACU0EG0ABR@FBGA107 [DX5028]
H8BCS0CE0ABR56M@FBGA107 [DX5028]
H8BCS0CG0MBR@FBGA107 [DX5028]
H8BCS0CH0MMR@FBGA130 [DX5140]
H8BCS0PE0MBR@FBGA107 [DX5028]
H8BCS0PG0MBP@FBGA107 [DX5028]
H8BCS0PH0ACR@FBGA137 [DX5011-1]
H8BCS0PH0MCP@FBGA137 [DX5011-1]
H8BCS0QE0MBR@FBGA107 [DX5028]
H8BCS0QE0MMR@FBGA130 [DX5140]
H8BCS0QG0ABR@FBGA107 [DX5028]
H8BCS0QG0MBP@FBGA107 [DX5028]
H8BCS0QG0MMR@FBGA130 [DX5140]
H8BCS0RJ0MCP@FBGA137 [DX5011]
H8BCS0SI0MAP@FBGA149 [DX5030]
H8BCS0SI0MBR@FBGA107 [DX5028]
H8BCS0SJ0BCR@FBGA137 [DX5011-1]
H8BCS0SJ0MCP@FBGA137 [DX5011]
H8BCS0SM0MBR@FBGA107 [DX5028]
H8BCS0UM0MER@FBGA107 [DX5028]
H8BCS0UN0MCR@FBGA137 [DX5011]
H8BES0SQ0MCR@FBGA137 [DX5011]
H8BES0UQ0MCR@FBGA137 [DX5011-1]
H8BES0UU0MCR@FBGA137 [DX5011-1]
H8BFS0WU0MCR@FBGA137 [DX5011]
H8KDS0UN0MER@FBGA168 [DX5205]
H8KES0XU0MRR@FBGA240 [DX5185]
H8KFS0YU0MRRS@FBGA240 [DX5185]
H9DA1GG25HAMBR@FBGA107 [DX5028]
H9DA1GG51HAMBR@FBGA107 [DX5028]
H9DA1GG51JBMCR@FBGA137 [DX5011]
H9DA1GH25HAMBR@FBGA107 [DX5028]
H9DA1GH25HAMMR@FBGA130 [DX5140]
H9DA1GH51HAMMR@FBGA130 [DX5140]
H9DA1GH51HBMBR@FBGA107 [DX5028]
H9DA1GH51JAMCR@FBGA137 [DX5011]
H9DA1GH51JMMMR@FBGA130 [DX5140]
H9DA2GG1GJAMCR@FBGA137 [DX5011]
H9DA2GG1GJMMMR@FBGA130 [DX5140]
H9DA2GH1GHAMBR@FBGA107 [DX5028]
H9DA4GH2GHAMER@FBGA107 [DX5028]
H9DA4GH2GJAMCR@FBGA137 [DX5011-1]
H9DA4GH4JJAMCR@FBGA137 [DX5011-1]
H9DA4VH2GJMMCR@FBGA137 [DX5011]
H9DA4VH4JJMMCR@FBGA137 [DX5011]
H9DA8HH4JJAMCR@FBGA137 [DX5011]
H9DP32A4JJACGR(1G)@FBGA153 [DX5104-1]
H9DP32A4JJACGR(20M)@FBGA153 [DX5104-1]
H9DP32A4JJACGR(2G)@FBGA153 [DX5104-1]
H9DP32A4JJMCGR(20M)@FBGA153 [DX5104-1]
H9DP32A4JJMCGR(2G)@FBGA153 [DX5104-1]
H9LA1GG25LBMCR@FBGA137 [DX5011]
H9LA1GG51JMMMR@FBGA130 [DX5140]
H9LA25G25HAMBR@FBGA107 [DX5028]
H9LA2GH1GJCM@FBGA137 [DX5011-1]
HY2764 [DX0001]
HY27C64A [DX0001]

HY27SF081G2A@FBGA63 [DX5046]
HY27UA081G1M@TSOP48 [DX1004]
HY27UF081G2A@FBGA63 [DX5046]
HY27UF081G2A@TSOP48 [DX1004-3]
HY27UF081G2M@TSOP48 [DX1004]
HY27UF082G2A@TSOP48 [DX1004]
HY27UF082G2B@FBGA63 [DX5046]
HY27UF082G2B@TSOP48 [DX1004-1]
HY27UF082G2M@TSOP48 [DX1004]
HY27UF084G2B@TSOP48 [DX1004-3]
HY27UF084G2M@TSOP48 [DX1004]
HY27UG088G5B@TSOP48 [DX1004]
HY27UG088G5M@TSOP48 [DX1004]
HY27US08121A@FBGA63 [DX5046]
HY27US08121A@TSOP48 [DX1004]
HY27US08121B@TSOP48 [DX1004]
HY27US08121M@TSOP48 [DX1004]
HY27US081G1M@USOP48 [DX1042]
HY27US08281A@TSOP48 [DX1004]
HY27US08561A@TSOP48 [DX1004]
HY27US08561A@WSOP48 [DX1042]
HY27US08561M@TSOP48 [DX1004]
HY27UT084G2A@TSOP48 [DX1004]
HY27UT084G2M@TSOP48 [DX1004]
HY27UT088G2A@TSOP48 [DX1004]
HY27UT088G2M@TSOP48 [DX1004]
HY27UU088G5M@TSOP48 [DX1004-1]
HY27UV08BG5M@TSOP48 [DX1004]
HY29DL162BF@FBGA48 [DX5022]
HY29DL162BT@TSOP48 [DX1004]
HY29DL162TF@FBGA48 [DX5022]
HY29DL162TT@TSOP48 [DX1004]
HY29DL163BF@FBGA48 [DX5022]
HY29DL163BT@TSOP48 [DX1004]
HY29DL163TF@FBGA48 [DX5022]
HY29DL163TT@TSOP48 [DX1004]
HY29DS162BF@FBGA48 [DX5022]
HY29DS162BT@TSOP48 [DX1004]
HY29DS162TF@FBGA48 [DX5022]
HY29DS162TT@TSOP48 [DX1004]
HY29DS163BF@FBGA48 [DX5022]
HY29DS163BT@TSOP48 [DX1004]
HY29DS163TF@FBGA48 [DX5022]
HY29DS163TT@TSOP48 [DX1004]
HY29F002T [DX0001]
HY29F002T@PLCC32 [DX2032]
HY29F002T@TSOP32 [DX1002]
HY29F040 [DX0001]
HY29F040@PLCC32 [DX2032]
HY29F040@TSOP32 [DX1002]
HY29F040A [DX0001]
HY29F040A@PLCC32 [DX2032]
HY29F040A@TSOP32 [DX1002]
HY29F080@TSOP40 [DX1006]
HY29F200B@PSOP44 [DX1014]
HY29F200B@TSOP48 [DX1004]
HY29F200T@PSOP44 [DX1014]
HY29F200T@TSOP48 [DX1004]
HY29F400ABG@PSOP44 [DX1014]
HY29F400ABT@TSOP48 [DX1004]
HY29F400ATG@PSOP44 [DX1014]
HY29F400ATT@TSOP48 [DX1004]
HY29F400BG@PSOP44 [DX1014]
HY29F400BT@TSOP48 [DX1004]
HY29F400TG@PSOP44 [DX1014]
HY29F400TT@TSOP48 [DX1004]
HY29F800ABG@PSOP44 [DX1014]
HY29F800ABT@TSOP48 [DX1004]
HY29F800ATG@PSOP44 [DX1014]
HY29F800ATT@TSOP48 [DX1004]
HY29F800BG@PSOP44 [DX1014]
HY29F800BT@TSOP48 [DX1004]
HY29F800TG@PSOP44 [DX1014]
HY29F800TT@TSOP48 [DX1004]
HY29LV160BF@FBGA48 [DX5022]
HY29LV160BT@TSOP48 [DX1004]
HY29LV160TF@FBGA48 [DX5022]
HY29LV160TT@TSOP48 [DX1004]
HY29LV320BF@FBGA48 [DX50UN]
HY29LV320BF@FBGA63 [DX5047]
HY29LV320BT@TSOP48 [DX1004]
HY29LV320TF@FBGA48 [DX50UN]
HY29LV320TF@FBGA63 [DX5047]
HY29LV320TT@TSOP48 [DX1004]
HY29LV400BF@FBGA48 [DX5002]
HY29LV400BT@TSOP48 [DX1004]
HY29LV400TF@FBGA48 [DX5002]
HY29LV400TT@TSOP48 [DX1004]
HY29LV800BF@FBGA48 [DX5002]
HY29LV800BG@PSOP44 [DX1014]
HY29LV800BT@TSOP48 [DX1004]
HY29LV800TF@FBGA48 [DX5002]
HY29LV800TG@PSOP44 [DX1014]
HY29LV800TT@TSOP48 [DX1004]
HY93C46 [DX0001]
HY93C46@SOIC8 [DX1045]

HY93C56 [DX0001]
HY93C56@SOIC8 [DX1045]
HY93C66 [DX0001]
HY93C66@SOIC8 [DX1045]
HY93C76 [DX0001]
HY93C76@SOIC8 [DX1045]
HY93C86 [DX0001]
HY93C86@SOIC8 [DX1045]
HYC0SEE0MF1P@FBGA149 [DX5030]
HYC0SEF0MF3P@FBGA137 [DX5011]
HYC0SEH0AF3P@FBGA137 [DX5011]
HYC0SEH0MF3P@FBGA137 [DX5011]
HYC0SGH0MF3P@FBGA137 [DX5011]
HYC0UEE0AF2P@FBGA107 [DX5028]
HYC0UEE0MF2P@FBGA107 [DX5028]
HYC0UEF0AF3P@FBGA137 [DX5011]
HYC0UEF0MF3P@FBGA137 [DX5011]
HYC0UEL0MF3R@FBGA137 [DX5011]
HYD0SEE0MF2P@FBGA107 [DX5028]
HYD0SFE0AF1P@FBGA149 [DX5030]
HYD0SFE0BF1P@FBGA149 [DX5030]
HYD0SFG0MF1P@FBGA149 [DX5030]
HYD0SQG0MF1P@FBGA149 [DX5030]
HYG0SEG0MF2P@FBGA107 [DX5028]
HYG0SGH0MF3P@FBGA137 [DX5011]
HYG0SGJ0MF3P@FBGA137 [DX5011]
HYG0UEE0MF2P@FBGA107 [DX5028]
HYG0UEG0MF2P@FBGA107 [DX5028]
HYG0UGH0MF3P(716A)@FBGA137 [DX5011]
HYG0UGH0MF3P(726A)@FBGA137 [DX5011]
HYH0SQJ0MF3P@FBGA137 [DX5011]
HYH0SSJ0MF3P@FBGA137 [DX5011]
HYI0SIJ0MF3P@FBGA137 [DX5011]
HYI0UIJ0MF3P@FBGA137 [DX5011]
MTC0UEF0CF3P@FBGA137 [DX5011]

DRAM & SRAM

HY62256A [DX0001]
HY62256A@TSOP28 [DX1001]
HY6264A [DX0001]
HY6264A@TSOP28 [DX1001]

MICROCONTROLLER

GMS34004TK [DX0001]
GMS34004TM [DX0001]
GMS34004TW [DX0001]
GMS34112TK [DX0001]
GMS34112TK@SOIC20 [DX1033]
GMS34112TK@SSOP20 [DX1026]
GMS34140TK [DX0001]
GMS34140TK@SOIC24 [DX1033]
GMS81004(dip20) [DX0001]
GMS81004(dip24) [DX0001]
GMS81004(dip28) [DX0001]
GMS81004@PLCC44 [DX2044]
GMS81004@SOIC20 [DX1033]
GMS81004@SOIC24 [DX1033]
GMS81004@SOIC28 [DX1033]
GMS81008(dip20) [DX0001]
GMS81008(dip24) [DX0001]
GMS81008(dip28) [DX0001]
GMS81008@PLCC44 [DX2044]
GMS81008@SOIC20 [DX1033]
GMS81008@SOIC24 [DX1033]
GMS81008@SOIC28 [DX1033]
GMS81016(dip20) [DX0001]
GMS81016(dip24) [DX0001]
GMS81016(dip28) [DX0001]
GMS81016@PLCC44 [DX2044]
GMS81016@SOIC20 [DX1033]
GMS81016@SOIC24 [DX1033]
GMS81016@SOIC28 [DX1033]
GMS81024(dip20) [DX0001]
GMS81024(dip24) [DX0001]
GMS81024(dip28) [DX0001]
GMS81024@PLCC44 [DX2044]
GMS81024@SOIC20 [DX1033]
GMS81024@SOIC24 [DX1033]
GMS81024@SOIC28 [DX1033]
GMS81032(dip20) [DX0001]
GMS81032(dip24) [DX0001]

GMS81032(dip28) [DX0001]
GMS81032@PLCC44 [DX2044]
GMS81032@SOIC20 [DX1033]
GMS81032@SOIC24 [DX1033]
GMS81032@SOIC28 [DX1033]
GMS81504AT [DX0032]
GMS81504T [DX0032]
GMS81516 [DX0001]
GMS81516@LQFP64 [DX3011]
GMS81516@MQFP64 [DX3015]
GMS81516@SDIP64 [DX0064]
GMS81516AT [DX0001]
GMS81516AT@LQFP64 [DX3011]
GMS81516AT@MQFP64 [DX3015]
GMS81516AT@SDIP64 [DX0064]
GMS81516BT [DX0001]
GMS81516BT@LQFP64 [DX3011]
GMS81516BT@MQFP64 [DX3015]
GMS81516BT@SDIP64 [DX0064]
GMS81524 [DX0001]
GMS81524@LQFP64 [DX3011]
GMS81524@MQFP64 [DX3015]
GMS81524@SDIP64 [DX0064]
GMS81524AT [DX0001]
GMS81524AT@LQFP64 [DX3011]
GMS81524AT@MQFP64 [DX3015]
GMS81524AT@SDIP64 [DX0064]
GMS81524BT [DX0001]
GMS81524BT@LQFP64 [DX3011]
GMS81524BT@MQFP64 [DX3015]
GMS81524BT@SDIP64 [DX0064]
GMS81604T [DX0001]
GMS81604T@PLCC44 [DX2044]
GMS81604T@SDIP42 [DX0042]
GMS81608T [DX0001]
GMS81608T@PLCC44 [DX2044]
GMS81608T@SDIP42 [DX0042]
GMS81C5016(dip28) [DX0001]
GMS81C5016(dip40) [DX0001]
GMS81C5016@PLCC44 [DX2044]
GMS81C5016@SOIC28 [DX1033]
GMS81C5016@TQFP44 [DX3002]
GMS81C5024(dip28) [DX0001]
GMS81C5024(dip40) [DX0001]
GMS81C5024@PLCC44 [DX2044]
GMS81C5024@SOIC28 [DX1033]
GMS81C5024@TQFP44 [DX3002]
GMS81C5032(dip28) [DX0001]
GMS81C5032(dip40) [DX0001]
GMS81C5032@PLCC44 [DX2044]
GMS81C5032@SOIC28 [DX1033]
GMS81C5032@TQFP44 [DX3002]
GMS82516T [DX0001]
GMS82516T@LQFP64 [DX3011]
GMS82516T@MQFP44 [DX3002]
GMS82516T@MQFP64 [DX3015]
GMS82516T@SDIP42 [DX0042]
GMS82516T@SDIP64 [DX0064]
GMS82524T [DX0001]
GMS82524T@LQFP64 [DX3011]
GMS82524T@MQFP44 [DX3002]
GMS82524T@MQFP64 [DX3015]
GMS82524T@SDIP42 [DX0042]
GMS82524T@SDIP64 [DX0064]
GMS84512T@SDIP52 [DX0056]
GMS84524T@SDIP52 [DX0056]
GMS87C1102 [DX0001]
GMS87C1102@SOP16 [DX1033]
GMS87C1202 [DX0001]
GMS87C1202@SOP20 [DX1033]
GMS87C1404 [DX0001]
GMS87C1404@SOP28 [DX1033]
GMS87C1408 [DX0001]
GMS87C1408@SOP28 [DX1033]
GMS87C2020@LQFP64 [DX3011]
GMS87C2020@MQFP64 [DX3015]
GMS87C2020@SDIP64 [DX0064]
GMS87C5032(dip28) [DX0001]
GMS87C5032(dip40) [DX0001]
GMS87C5032@PLCC44 [DX2044]
GMS87C5032@SOIC28 [DX1033]
GMS87C5032@TQFP44 [DX3002]
GMS87C5108@PQFP80 [DX3019]
GMS87C7008@LQFP64 [DX3011]
GMS87C7008@MQFP64 [DX3015]
GMS87C7008@SDIP64 [DX0064]
GMS87C7016@LQFP64 [DX3011]
GMS87C7016@MQFP64 [DX3015]
GMS87C7016@SDIP64 [DX0064]
GMS97C1051 [DX0001]
GMS97C1051@SOIC20 [DX1033]
GMS97C2051 [DX0001]
GMS97C2051@SOIC20 [DX1033]
GMS97C51 [DX0001]
GMS97C51@PLCC44 [DX2044]
GMS97C51@TQFP44 [DX3002]

GMS97C52 [DX0001]
GMS97C52@PLCC44 [DX2044]
GMS97C52@TQFP44 [DX3002]
GMS97C54 [DX0001]
GMS97C54@PLCC44 [DX2044]
GMS97C54@TQFP44 [DX3002]
GMS97C56 [DX0001]
GMS97C56@PLCC44 [DX2044]
GMS97C56@TQFP44 [DX3002]
GMS97C58 [DX0001]
GMS97C58@PLCC44 [DX2044]
GMS97C58@TQFP44 [DX3002]
GMS97L1051 [DX0001]
GMS97L1051@SOIC20 [DX1033]
GMS97L2051 [DX0001]
GMS97L2051@SOIC20 [DX1033]
GMS97L51 [DX0001]
GMS97L51@PLCC44 [DX2044]
GMS97L51@TQFP44 [DX3002]
GMS97L52 [DX0001]
GMS97L52@PLCC44 [DX2044]
GMS97L52@TQFP44 [DX3002]
GMS97L54 [DX0001]
GMS97L54@PLCC44 [DX2044]
GMS97L54@TQFP44 [DX3002]
GMS97L56 [DX0001]
GMS97L56@PLCC44 [DX2044]
GMS97L56@TQFP44 [DX3002]
GMS97L58 [DX0001]
GMS97L58@PLCC44 [DX2044]
GMS97L58@TQFP44 [DX3002]
GMS99C51 [DX0001]
GMS99C51@PLCC44 [DX2044]
GMS99C51@TQFP44 [DX3002]
GMS99C52 [DX0001]
GMS99C52@PLCC44 [DX2044]
GMS99C52@TQFP44 [DX3002]
GMS99C58 [DX0001]
GMS99C58@PLCC44 [DX2044]
GMS99C58@TQFP44 [DX3002]
HMS81004E(dip20) [DX0001]
HMS81004E(dip24) [DX0001]
HMS81004E(dip28) [DX0001]
HMS81004E@PLCC44 [DX2044]
HMS81004E@SOIC20 [DX1033]
HMS81004E@SOIC24 [DX1033]
HMS81004E@SOIC28 [DX1033]
HMS81008E(dip20) [DX0001]
HMS81008E(dip24) [DX0001]
HMS81008E(dip28) [DX0001]
HMS81008E@PLCC44 [DX2044]
HMS81008E@SOIC20 [DX1033]
HMS81008E@SOIC24 [DX1033]
HMS81008E@SOIC28 [DX1033]
HMS81016E(dip20) [DX0001]
HMS81016E(dip24) [DX0001]
HMS81016E(dip28) [DX0001]
HMS81016E@PLCC44 [DX2044]
HMS81016E@SOIC20 [DX1033]
HMS81016E@SOIC24 [DX1033]
HMS81016E@SOIC28 [DX1033]
HMS81020ET(dip20) [DX0001]
HMS81020ET(dip24) [DX0001]
HMS81020ET(dip28) [DX0001]
HMS81020ET@SOIC20 [DX1033]
HMS81020ET@SOIC24 [DX1033]
HMS81020ET@SOIC28 [DX1033]
HMS81020TL(dip20) [DX0001]
HMS81020TL(dip24) [DX0001]
HMS81020TL(dip28) [DX0001]
HMS81020TL@SOIC20 [DX1033]
HMS81020TL@SOIC24 [DX1033]
HMS81020TL@SOIC28 [DX1033]
HMS81024E(dip20) [DX0001]
HMS81024E(dip24) [DX0001]
HMS81024E(dip28) [DX0001]
HMS81024E@PLCC44 [DX2044]
HMS81024E@SOIC20 [DX1033]
HMS81024E@SOIC24 [DX1033]
HMS81024E@SOIC28 [DX1033]
HMS81032(dip20) [DX0001]
HMS81032(dip24) [DX0001]
HMS81032(dip28) [DX0001]
HMS81032@SOIC20 [DX1033]
HMS81032@SOIC24 [DX1033]
HMS81032@SOIC28 [DX1033]
HMS81032ET(dip20) [DX0001]
HMS81032ET(dip24) [DX0001]
HMS81032ET(dip28) [DX0001]
HMS81032ET@SOIC20 [DX1033]
HMS81032ET@SOIC24 [DX1033]
HMS81032ET@SOIC28 [DX1033]
HMS81032T(dip20) [DX0001]
HMS81032T(dip24) [DX0001]
HMS81032T(dip28) [DX0001]
HMS81032T@SOIC20 [DX1033]

HMS81032T@SOIC24 [DX1033]
HMS81032T@SOIC28 [DX1033]
HMS81032TL(dip20) [DX0001]
HMS81032TL(dip24) [DX0001]
HMS81032TL(dip28) [DX0001]
HMS81032TL@SOIC20 [DX1033]
HMS81032TL@SOIC24 [DX1033]
HMS81032TL@SOIC28 [DX1033]
HMS87C1102A [DX0001]
HMS87C1102A@SOP16 [DX1033]
HMS87C1104A [DX0001]
HMS87C1104A@SOP16 [DX1033]
HMS87C1202A [DX0001]
HMS87C1202A@SOP20 [DX1033]
HMS87C1204A [DX0001]
HMS87C1204A@SOP20 [DX1033]
HMS87C1302A@SDIP24 [DX0032]
HMS87C1302A@SOP24 [DX1033]
HMS87C1304A@SDIP24 [DX0032]
HMS87C1304A@SOP24 [DX1033]
HMS87C1404B [DX0001]
HMS87C1404B@SDIP28 [DX0032]
HMS87C1404B@SOIC28 [DX1033]
HMS87C1408B [DX0001]
HMS87C1408B@SDIP28 [DX0032]
HMS87C1408B@SOIC28 [DX1033]
HMS87C1416B [DX0001]
HMS87C1416B@SDIP28 [DX0032]
HMS87C1416B@SOIC28 [DX1033]
HMS87C1508B [DX0001]
HMS87C1516B [DX0001]
HMS87C1608B [DX0001]
HMS87C1616B [DX0001]
HMS87C1708B@SDIP42 [DX0042]
HMS87C1716B@SDIP42 [DX0042]
HMS87C1808B@TQFP44 [DX3002]
HMS87C1816B@TQFP44 [DX3002]
HMS87C5216 [DX0001]
HMS87C5216@PLCC44 [DX2044]
HMS87C5216@SOIC28 [DX1033]
HMS87C5216@TQFP44 [DX3002]
HMS99C51 [DX0001]
HMS99C51@PLCC44 [DX2044]
HMS99C51@TQFP44 [DX3002]
HMS99C52 [DX0001]
HMS99C52@PLCC44 [DX2044]
HMS99C52@TQFP44 [DX3002]
HMS99C58 [DX0001]
HMS99C58@PLCC44 [DX2044]
HMS99C58@TQFP44 [DX3002]

HYNIX(HYUNDAI)

PLD

HY18CV8J@PLCC20 [DX2020]
HY18CV8P [DX0001]
HY18CV8S@SOIC20 [DX1033]
HY18CV8T@TSOP20 [DX1000]

HYNIX-CUSTOMER

E(E)PROM/FRAM/NVRAM

H26M32001DAR(INTEL)(20M)@FBGA169 [DX5158]
H26M32001DAR(INTEL)@FBGA169 [DX5158]
H26M44001CAR(INTEL)(20M)@FBGA169 [DX5158]
H26M44001CAR(INTEL)@FBGA169 [DX5158]
H26M54001AJR(INTEL)(20M)@FBGA169 [DX5158]
H26M54001AJR(INTEL)@FBGA169 [DX5158]
H26M54001DQR(INTEL)(20M)@FBGA169 [DX5158]
H26M54001DQR(INTEL)@FBGA169 [DX5158]
H26M64002DQRS(INTEL)(20M)@BGA169 [DX5158]

H26M64002DQRS(INTEL)@BGA169 [DX5158]
H26M64003DQR(INTEL)(20M)@BGA169 [DX5158]
H26M64003DQR(INTEL)@BGA169 [DX5158]
H26M68001MNR(INTEL)(20M)@FBGA169 [DX5158]
H26M68001MNR(INTEL)@FBGA169 [DX5158]
H27U1G8F2BFR(ST)@FBGA63 [DX5046]
H27U1G8F2BFR@FBGA63(MOTOROLA) [DX5046]
H27U1G8F2BTR(X-Y)@TSOP48 [DX1004-1]
H27U1G8F2BTR@TSOP48(BATM) [DX1004-1]
H27U1G8F2BTR@TSOP48(DaXian) [DX1004-1]
H27U1G8F2BTR@TSOP48(MOTOROLA) [DX1004-1]
H27U2G8F2CTR(TRIDENT)@TSOP48 [DX1004-1]
H27U4G8F2DTR(YH)@TSOP48 [DX1004-1]
H27U518S2CTR(CHUANGJIA)@TSOP48 [DX1004]
H8ACS0CE0ABR56M(FOXCONN)@FBGA107 [DX5028]
H8ACS0CF0MMR@FBGA130 [DX5130]
H8ACS0PE0MBR(NVIDIA)@FBGA107 [DX5028]
H8ACS0PE0MBR(TD)@FBGA107 [DX5028]
H8ACS0PG0ABR(TD1)@FBGA107 [DX5028]
H8ACS0PG0MBP(TD)@FBGA107 [DX5028]
H8ACS0PG0MBP(TD1)@FBGA107 [DX5028]
H8ACS0SI0MBR(ZTE)@FBGA107 [DX5028]
H8BCS0CE0ABR56M(ZTE)@FBGA107 [DX5028]
H8BCS0PE0MBR(ICERA)@FBGA107 [DX5028]
H8BCS0PH0ACR(XSR1.0)@FBGA137 [DX5011]
H8BCS0QE0MBR(ICERA)@FBGA107 [DX5028]
H8BCS0QE0MMR(ICERA)@FBGA130 [DX5140]
H8BCS0QE0MMR(XSR1.0)@FBGA130 [DX5140]
H8BCS0QG0ABR(MLT-XY)@FBGA107 [DX5028]
H8BCS0QG0MBP(M310-LQ)@FBGA107 [DX5028]
H8BCS0QG0MMR(INVENTEC)@FBGA130 [DX5140]
H8BCS0SI0MBR(HIFFS)@FBGA107 [DX5028]
H8BCS0SI0MBR(M310-LQ)@FBGA107 [DX5028]
H8BCS0SI0MBR(MLT-XY)@FBGA107 [DX5028]
H8BCS0SM0MBR(GOSO)@FBGA107 [DX5028]
H8BCS0UN0MCR(LG)@FBGA137 [DX5011]
H8BES0UU0MCR(XY)@FBGA137 [DX5011]
H8BES0UU0MCR(ZTE)@FBGA137 [DX5011]
H9DA1GH25HAMMR(ICERA)@FBGA107 [DX5140]
H9DA1GH25HAMMR(SBM2)@FBGA130 [DX5140]
H9DA2GG1GJAMCR(FREESCALE)@BGA137 [DX5011-1]
H9DA4GH2GHAMER(M310)@FBGA107 [DX5028]
H9DA4GH4JJAMCR(XY)@FBGA137 [DX5011]
H9DA4GH4JJAMCR(ZTE)@FBGA137 [DX5011]
HY27UF081G2A(AMLOGIC)@TSOP48 [DX1004]
HY27UF081G2A(ORB)@TSOP48 [DX1004]
HY27UF081G2A(ZTE)@FBGA63 [DX5046]
HY27UF081G2A(ZX)@TSOP48 [DX1043]

HY27UF082G2A(AMLOGIC)@TSOP48 [DX1004]
HY27UF082G2A(UT)@TSOP48 [DX1004]
HY27UF082G2B(DaXian)@TSOP48 [DX1004-1]
HY27UF082G2B(HUAWEI)@TSOP48 [DX1004-1]
HY27UF082G2B(INSPUR)@TSOP48 [DX1004-1]
HY27UF082G2B(RT)@TSOP48 [DX1004-1]
HY27UF082G2B(SBM)@TSOP48 [DX1004-1]
HY27UF082G2B(SP)@TSOP48 [DX1004-3]
HY27UF082G2B(ST7141)@TSOP48 [DX1004-1]
HY27UF082G2B(TRIDENT)@TSOP48 [DX1004-1]
HY27UF082G2B(UT)@TSOP48 [DX1004-1]
HY27UF082G2B(WHL)@TSOP48 [DX1004-1]
HY27UF082G2M(ZX)@TSOP48 [DX1043]
HY27UF084G2B(HUAWEI)@TSOP48 [DX1004-1]
HY27UF084G2B(READ-BAD)@TSOP48 [DX1004-1]
HY27UF084G2B(YH)@TSOP48 [DX1004-1]
HY27UF084G2M(HUAWEI)@TSOP48 [DX1004]
HY27UF084G2M(READ-BAD)@TSOP48 [DX1004-1]
HY27UF084G2M(YH)@TSOP48 [DX1004] HY27US08121B(HD)@TSOP48 [DX1004]
HY27US08121B(LG)@TSOP48 [DX1004]
HY27US08121B(LGE02)@TSOP48 [DX1004]
HY27UT084G2A(AMLOGIC)@TSOP48 [DX1004]
HYC0SEH0AF3P(DATACODE)@FBGA137 [DX5011]
HYC0UEE0AF2P(TXT)@FBGA107 [DX5028]
HYC0UEE0MF2P(TXT)@FBGA107 [DX5028]
HYH0SQJ0MF3P(MLT-XY)@FBGA137 [DX5011]

HYUNDAI

E(E)PROM/FRAM/NVRAM

HY2764 [DX0001]
HY29DL162BF@FBGA48 [DX5022]
HY29DL162TF@FBGA48 [DX5022]
HY29DL163BF@FBGA48 [DX5022]
HY29DL163TF@FBGA48 [DX5022]
HY29DS162BF@FBGA48 [DX5022]
HY29DS162TF@FBGA48 [DX5022]
HY29DS163BF@FBGA48 [DX5022]
HY29DS163TF@FBGA48 [DX5022]
HY29F002T [DX0001]
HY29F002T@TSOP32 [DX1002]
HY29F040@PLCC32 [DX2032]
HY29F040A [DX0001]
HY29F040A@TSOP32 [DX1002]
HY29F200B@PSOP44 [DX1014]
HY29F200T@PSOP44 [DX1014]
HY27C64A [DX0001]
HY29DL162BT@TSOP48 [DX1004]
HY29DL162TT@TSOP48 [DX1004]
HY29DL163BT@TSOP48 [DX1004]
HY29DL163TT@TSOP48 [DX1004]
HY29DS162BT@TSOP48 [DX1004]
HY29DS162TT@TSOP48 [DX1004]
HY29DS163BT@TSOP48 [DX1004]
HY29DS163TT@TSOP48 [DX1004]
HY29F002T@PLCC32 [DX2032]
HY29F040 [DX0001]
HY29F040@TSOP32 [DX1002]
HY29F040A@PLCC32 [DX2032]
HY29F080@TSOP40 [DX1006]
HY29F200B@TSOP48 [DX1004]
HY29F200T@TSOP48 [DX1004]

HY29F400ABG@PSOP44 [DX1014]
HY29F400ABT@TSOP48 [DX1004]
HY29F400ATG@PSOP44 [DX1014]
HY29F400ATT@TSOP48 [DX1004]
HY29F400BG@PSOP44 [DX1014]
HY29F400BT@TSOP48 [DX1004]
HY29F400TG@PSOP44 [DX1014]
HY29F400TT@TSOP48 [DX1004]
HY29F800ABG@PSOP44 [DX1014]
HY29F800ABT@TSOP48 [DX1004]
HY29F800ATG@PSOP44 [DX1014]
HY29F800ATT@TSOP48 [DX1004]
HY29F800BG@PSOP44 [DX1014]
HY29F800BT@TSOP48 [DX1004]
HY29F800TG@PSOP44 [DX1014]
HY29F800TT@TSOP48 [DX1004]
HY29LV160BF@FBGA48 [DX5022]
HY29LV160BT@TSOP48 [DX1004]
HY29LV160TF@FBGA48 [DX5022]
HY29LV160TT@TSOP48 [DX1004]
HY29LV320BF@FBGA48 [DX50UN]
HY29LV320BF@FBGA63 [DX5047]
HY29LV320BT@TSOP48 [DX1004]
HY29LV320TF@FBGA48 [DX50UN]
HY29LV320TF@FBGA63 [DX5047]
HY29LV320TT@TSOP48 [DX1004]
HY29LV400BF@FBGA48 [DX5002]
HY29LV400BT@TSOP48 [DX1004]
HY29LV400TF@FBGA48 [DX5002]
HY29LV400TT@TSOP48 [DX1004]
HY29LV800BF@FBGA48 [DX5002]
HY29LV800BG@PSOP44 [DX1014]
HY29LV800BT@TSOP48 [DX1004]
HY29LV800TF@FBGA48 [DX5002]
HY29LV800TG@PSOP44 [DX1014]
HY29LV800TT@TSOP48 [DX1004]
HY93C46 [DX0001]
HY93C46@SOIC8 [DX1045]
HY93C56 [DX0001]
HY93C56@SOIC8 [DX1045]
HY93C66 [DX0001]
HY93C66@SOIC8 [DX1045]
HY93C76 [DX0001]
HY93C76@SOIC8 [DX1045]
HY93C86 [DX0001]
HY93C86@SOIC8 [DX1045]

DRAM & SRAM

HY62256A [DX0001]
HY62256A@TSOP28 [DX1001]
HY6264A [DX0001]
HY6264A@TSOP28 [DX1001]

MICROCONTROLLER

GMS34004TK [DX0001]
GMS34004TM [DX0001]
GMS34004TW [DX0001]
GMS34112TK [DX0001]
GMS34112TK@SOIC20 [DX1033]
GMS34112TK@SSOP20 [DX1026]
GMS34140TK [DX0001]
GMS34140TK@SOIC24 [DX1033]
GMS81004(dip20) [DX0001]
GMS81004(dip24) [DX0001]
GMS81004(dip28) [DX0001]
GMS81004@PLCC44 [DX2044]
GMS81004@SOIC20 [DX1033]
GMS81004@SOIC24 [DX1033]
GMS81004@SOIC28 [DX1033]
GMS81008(dip20) [DX0001]
GMS81008(dip24) [DX0001]
GMS81008(dip28) [DX0001]
GMS81008@PLCC44 [DX2044]
GMS81008@SOIC20 [DX1033]
GMS81008@SOIC24 [DX1033]
GMS81008@SOIC28 [DX1033]
GMS81016(dip20) [DX0001]
GMS81016(dip24) [DX0001]
GMS81016(dip28) [DX0001]
GMS81016@PLCC44 [DX2044]
GMS81016@SOIC20 [DX1033]
GMS81016@SOIC24 [DX1033]
GMS81016@SOIC28 [DX1033]
GMS81024(dip20) [DX0001]

GMS81024(dip24) [DX0001]
GMS81024@PLCC44 [DX2044]
GMS81024@SOIC24 [DX1033]
GMS81032(dip20) [DX0001]
GMS81032(dip28) [DX0001]
GMS81032@SOIC20 [DX1033]
GMS81032@SOIC28 [DX1033]
GMS81504T [DX0032]
GMS81516@LQFP64 [DX3011]
GMS81516@SDIP64 [DX0064]
GMS81516AT@LQFP64 [DX3011]
GMS81516AT@SDIP64 [DX0064]
GMS81516BT@LQFP64 [DX3011]
GMS81516BT@SDIP64 [DX0064]
GMS81524@LQFP64 [DX3011]
GMS81524@SDIP64 [DX0064]
GMS81524AT@LQFP64 [DX3011]
GMS81524AT@SDIP64 [DX0064]
GMS81524BT@LQFP64 [DX3011]
GMS81524BT@SDIP64 [DX0064]
GMS81604T@PLCC44 [DX2044]
GMS81608T [DX0001]
GMS81608T@SDIP42 [DX0042]
GMS81C5016(dip40) [DX0001]
GMS81C5016@SOIC28 [DX1033]
GMS81C5024(dip28) [DX0001]
GMS81C5024@PLCC44 [DX2044]
GMS81C5024@TQFP44 [DX3002]
GMS81C5032(dip40) [DX0001]
GMS81C5032@SOIC28 [DX1033]
GMS82516T [DX0001]
GMS82516T@MQFP44 [DX3002]
GMS82516T@SDIP42 [DX0042]
GMS82524T [DX0001]
GMS82524T@MQFP44 [DX3002]
GMS82524T@SDIP42 [DX0042]
GMS84512T@SDIP52 [DX0056]
GMS87C1102 [DX0001]
GMS87C1202 [DX0001]
GMS87C1404 [DX0001]
GMS87C1408 [DX0001]
GMS87C2020@LQFP64 [DX3011]
GMS87C2020@SDIP64 [DX0064]
GMS87C5032(dip40) [DX0001]
GMS87C5032@SOIC28 [DX1033]
GMS87C5108@PQFP80 [DX3019]
GMS87C7008@MQFP64 [DX3015]
GMS87C7016@LQFP64 [DX3011]
GMS81024(dip28) [DX0001]
GMS81024@SOIC20 [DX1033]
GMS81024@SOIC28 [DX1033]
GMS81032(dip24) [DX0001]
GMS81032@PLCC44 [DX2044]
GMS81032@SOIC24 [DX1033]
GMS81504AT [DX0032]
GMS81516 [DX0001]
GMS81516@MQFP64 [DX3015]
GMS81516AT [DX0001]
GMS81516AT@MQFP64 [DX3015]
GMS81516BT [DX0001]
GMS81516BT@MQFP64 [DX3015]
GMS81524 [DX0001]
GMS81524@MQFP64 [DX3015]
GMS81524AT [DX0001]
GMS81524AT@MQFP64 [DX3015]
GMS81524BT [DX0001]
GMS81524BT@MQFP64 [DX3015]
GMS81604T [DX0001]
GMS81604T@SDIP42 [DX0042]
GMS81608T@PLCC44 [DX2044]
GMS81C5016(dip28) [DX0001]
GMS81C5016@PLCC44 [DX2044]
GMS81C5016@TQFP44 [DX3002]
GMS81C5024(dip40) [DX0001]
GMS81C5024@SOIC28 [DX1033]
GMS81C5032(dip28) [DX0001]
GMS81C5032@PLCC44 [DX2044]
GMS81C5032@TQFP44 [DX3002]
GMS82516T@LQFP64 [DX3011]
GMS82516T@MQFP64 [DX3015]
GMS82516T@SDIP64 [DX0064]
GMS82524T@LQFP64 [DX3011]
GMS82524T@MQFP64 [DX3015]
GMS82524T@SDIP64 [DX0064]
GMS84524T@SDIP52 [DX0056]
GMS87C1102@SOP16 [DX1033]
GMS87C1202@SOP20 [DX1033]
GMS87C1404@SOP28 [DX1033]
GMS87C1408@SOP28 [DX1033]
GMS87C2020@MQFP64 [DX3015]
GMS87C5032(dip28) [DX0001]
GMS87C5032@PLCC44 [DX2044]
GMS87C5032@TQFP44 [DX3002]
GMS87C7008@LQFP64 [DX3011]
GMS87C7008@SDIP64 [DX0064]
GMS87C7016@MQFP64 [DX3015]

GMS87C7016@SDIP64 [DX0064]
GMS97C1051@SOIC20 [DX1033]
GMS97C2051@SOIC20 [DX1033]
GMS97C51@PLCC44 [DX2044]
GMS97C52 [DX0001]
GMS97C52@TQFP44 [DX3002]
GMS97C54@PLCC44 [DX2044]
GMS97C56 [DX0001]
GMS97C56@TQFP44 [DX3002]
GMS97C58@PLCC44 [DX2044]
GMS97L1051 [DX0001]
GMS97L2051 [DX0001]
GMS97L51 [DX0001]
GMS97L51@TQFP44 [DX3002]
GMS97L52@PLCC44 [DX2044]
GMS97L54 [DX0001]
GMS97L54@TQFP44 [DX3002]
GMS97L56@PLCC44 [DX2044]
GMS97L58 [DX0001]
GMS97L58@TQFP44 [DX3002]
GMS99C51@PLCC44 [DX2044]
GMS99C52 [DX0001]
GMS99C52@TQFP44 [DX3002]
GMS99C58@PLCC44 [DX2044]
HMS81004E(dip20) [DX0001]
HMS81004E(dip28) [DX0001]
HMS81004E@SOIC20 [DX1033]
HMS81004E@SOIC28 [DX1033]
HMS81008E(dip24) [DX0001]
HMS81008E@PLCC44 [DX2044]
HMS81008E@SOIC24 [DX1033]
HMS81016E(dip20) [DX0001]
HMS81016E(dip28) [DX0001]
HMS81016E@SOIC20 [DX1033]
HMS81016E@SOIC28 [DX1033]
HMS81020ET(dip24) [DX0001]
HMS81020ET@SOIC20 [DX1033]
HMS81020ET@SOIC28 [DX1033]
HMS81020TL(dip24) [DX0001]
HMS81020TL@SOIC20 [DX1033]
HMS81020TL@SOIC28 [DX1033]
HMS81024E(dip24) [DX0001]
HMS81024E@PLCC44 [DX2044]
HMS81024E@SOIC24 [DX1033]
HMS81032(dip20) [DX0001]
HMS81032(dip28) [DX0001]
HMS81032@SOIC24 [DX1033]
HMS81032ET(dip20) [DX0001]
GMS97C1051 [DX0001]
GMS97C2051 [DX0001]
GMS97C51 [DX0001]
GMS97C51@TQFP44 [DX3002]
GMS97C52@PLCC44 [DX2044]
GMS97C54 [DX0001]
GMS97C54@TQFP44 [DX3002]
GMS97C56@PLCC44 [DX2044]
GMS97C58 [DX0001]
GMS97C58@TQFP44 [DX3002]
GMS97L1051@SOIC20 [DX1033]
GMS97L2051@SOIC20 [DX1033]
GMS97L51@PLCC44 [DX2044]
GMS97L52 [DX0001]
GMS97L52@TQFP44 [DX3002]
GMS97L54@PLCC44 [DX2044]
GMS97L56 [DX0001]
GMS97L56@TQFP44 [DX3002]
GMS97L58@PLCC44 [DX2044]
GMS99C51 [DX0001]
GMS99C51@TQFP44 [DX3002]
GMS99C52@PLCC44 [DX2044]
GMS99C58 [DX0001]
GMS99C58@TQFP44 [DX3002]
HMS81004E(dip24) [DX0001]
HMS81004E@PLCC44 [DX2044]
HMS81004E@SOIC24 [DX1033]
HMS81008E(dip20) [DX0001]
HMS81008E(dip28) [DX0001]
HMS81008E@SOIC20 [DX1033]
HMS81008E@SOIC28 [DX1033]
HMS81016E(dip24) [DX0001]
HMS81016E@PLCC44 [DX2044]
HMS81016E@SOIC24 [DX1033]
HMS81020ET(dip20) [DX0001]
HMS81020ET(dip28) [DX0001]
HMS81020ET@SOIC24 [DX1033]
HMS81020TL(dip20) [DX0001]
HMS81020TL(dip28) [DX0001]
HMS81020TL@SOIC24 [DX1033]
HMS81024E(dip20) [DX0001]
HMS81024E(dip28) [DX0001]
HMS81024E@SOIC20 [DX1033]
HMS81024E@SOIC28 [DX1033]
HMS81032(dip24) [DX0001]
HMS81032@SOIC20 [DX1033]
HMS81032@SOIC28 [DX1033]
HMS81032ET(dip24) [DX0001]

HMS81032ET(dip28) [DX0001]
HMS81032ET@SOIC20 [DX1033]
HMS81032ET@SOIC24 [DX1033]
HMS81032ET@SOIC28 [DX1033]
HMS81032T(dip20) [DX0001]
HMS81032T(dip24) [DX0001]
HMS81032T(dip28) [DX0001]
HMS81032T@SOIC20 [DX1033]
HMS81032T@SOIC24 [DX1033]
HMS81032T@SOIC28 [DX1033]
HMS81032TL(dip20) [DX0001]
HMS81032TL(dip24) [DX0001]
HMS81032TL(dip28) [DX0001]
HMS81032TL@SOIC20 [DX1033]
HMS81032TL@SOIC24 [DX1033]
HMS81032TL@SOIC28 [DX1033]
HMS87C1102A [DX0001]
HMS87C1102A@SOP16 [DX1033]
HMS87C1104A [DX0001]
HMS87C1104A@SOP16 [DX1033]
HMS87C1202A [DX0001]
HMS87C1202A@SOP20 [DX1033]
HMS87C1204A [DX0001]
HMS87C1204A@SOP20 [DX1033]
HMS87C1302A@SDIP24 [DX0032]
HMS87C1302A@SOP24 [DX1033]
HMS87C1304A@SDIP24 [DX0032]
HMS87C1304A@SOP24 [DX1033]
HMS87C1404B [DX0001]
HMS87C1404B@SDIP28 [DX0032]
HMS87C1404B@SOIC28 [DX1033]
HMS87C1408B [DX0001]
HMS87C1408B@SDIP28 [DX0032]
HMS87C1408B@SOIC28 [DX1033]
HMS87C1416B [DX0001]
HMS87C1416B@SDIP28 [DX0032]
HMS87C1416B@SOIC28 [DX1033]
HMS87C1508B [DX0001]
HMS87C1516B [DX0001]
HMS87C1608B [DX0001]
HMS87C1616B [DX0001]
HMS87C1708B@SDIP42 [DX0042]
HMS87C1716B@SDIP42 [DX0042]
HMS87C1808B@TQFP44 [DX3002]
HMS87C1816B@TQFP44 [DX3002]
HMS87C5216 [DX0001]
HMS87C5216@PLCC44 [DX2044]
HMS87C5216@SOIC28 [DX1033]
HMS87C5216@TQFP44 [DX3002]
HMS99C51 [DX0001]
HMS99C51@PLCC44 [DX2044]
HMS99C51@TQFP44 [DX3002]
HMS99C52 [DX0001]
HMS99C52@PLCC44 [DX2044]
HMS99C52@TQFP44 [DX3002]
HMS99C58 [DX0001]
HMS99C58@PLCC44 [DX2044]
HMS99C58@TQFP44 [DX3002]

IC Microsystems

E(E)PROM/FRAM/NVRAM

X24C00 [DX0001]
X24C00@MSOP8 [DX1015]
X24C00@SOIC8 [DX1045]
X24C01 [DX0001]
X24C01@MSOP8 [DX1015]
X24C01@SOIC14 [DX1030]
X24C01@SOIC8 [DX1045]
X24C01A [DX0001]
X24C01A@MSOP8 [DX1015]
X24C01A@SOIC8 [DX1045]
X24C02 [DX0001]
X24C02@MSOP8 [DX1015]
X24C02@SOIC14 [DX1030]
X24C02@SOIC8 [DX1045]
X24C04 [DX0001]
X24C04@MSOP8 [DX1015]
X24C04@SOIC14 [DX1030]
X24C04@SOIC8 [DX1045]
X24C08 [DX0001]
X24C08@MSOP8 [DX1015]
X24C08@SOIC14 [DX1030]
X24C08@SOIC8 [DX1045]
X24C16 [DX0001]
X24C16@MSOP8 [DX1015]
X24C16@SOIC14 [DX1030]
X24C16@SOIC8 [DX1045]

ICE

E(E)PROM/FRAM/NVRAM

ICE25P05 [DX0001]
ICE25P05@SOIC8 [DX1045]
ICE27C010 [DX0001]
ICE27C010@PLCC32 [DX2032]
ICE27C010@TSOP32 [DX1002]
ICE27C020 [DX0001]
ICE27C020@PLCC32 [DX2032]
ICE27C020@TSOP32 [DX1002]
ICE27C512 [DX0001]
ICE27C512@PLCC32 [DX2032]
ICE27C512@TSOP28 [DX1024]
ICE27LC010 [DX0001]
ICE27LC010@PLCC32 [DX2032]
ICE27LC010@TSOP32 [DX1002]
ICE27LC020 [DX0001]
ICE27LC020@PLCC32 [DX2032]
ICE27LC020@TSOP32 [DX1002]
ICE27LC512 [DX0001]
ICE27LC512@PLCC32 [DX2032]
ICE27LC512@TSOP28 [DX1024]
ICE28LF010 [DX0001]
ICE28LF010@PLCC32 [DX2032]
ICE37C512 [DX0001]
ICE37C512@PLCC32 [DX2032]
ICE37C512@TSOP32 [DX1002]
ICE37LC512 [DX0001]
ICE37LC512@PLCC32 [DX2032]
ICE37LC512@TSOP32 [DX1002]

ICMIC

E(E)PROM/FRAM/NVRAM

X76F101 [DX0001]
X76F101@SOIC8 [DX1045]
X76F400@SOIC8 [DX1000]
X76F400@TSSOP8 [DX1000]

ICSI

E(E)PROM/FRAM/NVRAM

IC71V08F32AS04@FBGA64 [DX5026]
IC71V08F32AS04@FBGA73 [DX5026]
IC71V08F32AS08@FBGA64 [DX5026]
IC71V08F32AS08@FBGA73 [DX5026]
IC71V08F32BS04@FBGA64 [DX5026]
IC71V08F32BS04@FBGA73 [DX5026]
IC71V08F32BS08@FBGA64 [DX5026]
IC71V08F32BS08@FBGA73 [DX5026]
IC71V08F32CS04@FBGA64 [DX5026]
IC71V08F32CS04@FBGA73 [DX5026]
IC71V08F32CS08@FBGA64 [DX5026]
IC71V08F32CS08@FBGA73 [DX5026]
IC71V08F32DS04@FBGA64 [DX5026]
IC71V08F32DS04@FBGA73 [DX5026]
IC71V08F32DS08@FBGA64 [DX5026]
IC71V08F32DS08@FBGA73 [DX5026]
IC71V08F32ES04@FBGA64 [DX5026]
IC71V08F32ES04@FBGA73 [DX5026]
IC71V08F32ES08@FBGA64 [DX5026]
IC71V08F32ES08@FBGA73 [DX5026]
IC71V08F32FS04@FBGA64 [DX5026]
IC71V08F32FS04@FBGA73 [DX5026]
IC71V08F32FS08@FBGA64 [DX5026]
IC71V08F32FS08@FBGA73 [DX5026]
IC71V16F32AS04@FBGA64 [DX5026]
IC71V16F32AS04@FBGA73 [DX5026]
IC71V16F32AS08@FBGA64 [DX5026]
IC71V16F32AS08@FBGA73 [DX5026]

IC71V16F32BS04@FBGA64 [DX5026]
IC71V16F32BS08@FBGA64 [DX5026]
IC71V16F32CS04@FBGA64 [DX5026]
IC71V16F32CS08@FBGA64 [DX5026]
IC71V16F32DS04@FBGA64 [DX5026]
IC71V16F32DS08@FBGA64 [DX5026]
IC71V16F32ES04@FBGA64 [DX5026]
IC71V16F32ES08@FBGA64 [DX5026]
IC71V16F32FS04@FBGA64 [DX5026]
IC71V16F32FS08@FBGA64 [DX5026]
IC71V16F32GS04@FBGA73 [DX5001]
IC71V16F32HS04@FBGA73 [DX5001]
IC71V16F64IP16@FBGA73 [DX5001]
IC71V16F32BS04@FBGA73 [DX5026]
IC71V16F32BS08@FBGA73 [DX5026]
IC71V16F32CS04@FBGA73 [DX5026]
IC71V16F32CS08@FBGA73 [DX5026]
IC71V16F32DS04@FBGA73 [DX5026]
IC71V16F32DS08@FBGA73 [DX5026]
IC71V16F32ES04@FBGA73 [DX5026]
IC71V16F32ES08@FBGA73 [DX5026]
IC71V16F32FS04@FBGA73 [DX5026]
IC71V16F32FS08@FBGA73 [DX5026]
IC71V16F32GS08@FBGA73 [DX5001]
IC71V16F32HS08@FBGA73 [DX5001]
IC71V16F64IS08@FBGA73 [DX5001]

MICROCONTROLLER

IC89LV51A [DX0001]
IC89LV51A@TQFP44 [DX3002]
IC89LV52A@PLCC44 [DX2044]
IS89C51A [DX0001]
IS89C51A@TQFP44 [DX3002]
IS89C52A@PLCC44 [DX2044]
IS89C54 [DX0001]
IS89C54@TQFP44 [DX3002]
IS89C58@PLCC44 [DX2044]
IS89C64 [DX0001]
IS89C64@TQFP44 [DX3002]
IS89E54@PLCC44 [DX2044]
IS89E58 [DX0001]
IS89E58@TQFP44 [DX3002]
IS89E64@PLCC44 [DX2044]
IC89LV51A@PLCC44 [DX2044]
IC89LV52A [DX0001]
IC89LV52A@TQFP44 [DX3002]
IS89C51A@PLCC44 [DX2044]
IS89C52A [DX0001]
IS89C52A@TQFP44 [DX3002]
IS89C54@PLCC44 [DX2044]
IS89C58 [DX0001]
IS89C58@TQFP44 [DX3002]
IS89C64@PLCC44 [DX2044]
IS89E54 [DX0001]
IS89E54@TQFP44 [DX3002]
IS89E58@PLCC44 [DX2044]
IS89E64 [DX0001]
IS89E64@TQFP44 [DX3002]

ICT

E(E)PROM/FRAM/NVRAM

27CX010 [DX0001]
27CX010@TSOP32 [DX1002]
27CX321 [DX0001]
27CX641 [DX0001]
93C46 [DX0001]
93C46A [DX0001]
93C56A [DX0001]
93C66A [DX0001]
93CX46 [DX0001]
93CX56 [DX0001]
27CX010@PLCC32 [DX2032]
27CX256 [DX0001]
27CX322 [DX0001]
27CX642 [DX0001]
93C46@SOIC8 [DX1045]
93C46A@SOIC8 [DX1045]
93C56A@SOIC8 [DX1045]
93C66A@SOIC8 [DX1045]
93CX46@SOIC8 [DX1045]
93CX56@SOIC8 [DX1045]

93CX66 [DX0001]
93CX66@SOIC8 [DX1045]

PLD

PA7024 [DX0001]
PA7024(J)@PLCC28 [DX2028]
PA7024(JN)@PLCC28 [DX2028]
PA7024@SOIC24 [DX1033]
PA7140 [DX0001]
PA7140@PLCC44 [DX2044]
PA7140@TQFP44 [DX3003]
PA7540 [DX0001]
PA7540(J)@PLCC28 [DX2028]
PA7540(JN)@PLCC28 [DX2028]
PA7572 [DX0001]
PA7572@PLCC44 [DX2044]
PA7572@TQFP44 [DX3003]
PEEL153 [DX0001]
PEEL173 [DX0001]
PEEL18CV8J@PLCC20 [DX2020]
PEEL18CV8P [DX0001]
PEEL18CV8S@SOIC20 [DX1033]
PEEL18CV8T@TSOP20 [DX1000]
PEEL18CV8Z [DX0001]
PEEL18CV8Z@PLCC20 [DX2020]
PEEL18CV8Z@SOIC20 [DX1033]
PEEL18CV8Z@TSOP20 [DX1000]
PEEL18LV8Z [DX0001]
PEEL18LV8Z@PLCC20 [DX2020]
PEEL18LV8Z@SOIC20 [DX1033]
PEEL18LV8Z@TSOP20 [DX1000]
PEEL22CV10A [DX0001]
PEEL22CV10A@PLCC28 [DX2028]
PEEL22CV10A@SOIC24 [DX1033]
PEEL22CV10A@TSOP24 [DX1000]
PEEL22CV10A+ [DX0001]
PEEL22CV10A+@PLCC28 [DX2028]
PEEL22CV10A+@SOIC24 [DX1033]
PEEL22CV10A+@TSOP24 [DX1000]
PEEL22CV10A++ [DX0001]
PEEL22CV10A++@PLCC28 [DX2028]
PEEL22CV10A++@SOIC24 [DX1033]
PEEL22CV10A++@TSOP24 [DX1000]
PEEL22CV10AZ [DX0001]
PEEL22CV10AZ@PLCC28 [DX2028]
PEEL22CV10AZ@SOIC24 [DX1033]
PEEL22CV10AZ@TSOP24 [DX1000]
PEEL22CV10AZ+ [DX0001]
PEEL22CV10AZ+@PLCC28 [DX2028]
PEEL22CV10AZ+@SOIC24 [DX1033]
PEEL22CV10AZ+@TSOP24 [DX1000]
PEEL22CV10AZ++ [DX0001]
PEEL22CV10AZ++@PLCC28 [DX2028]
PEEL22CV10AZ++@SOIC24 [DX1033]
PEEL22CV10AZ++@TSOP24 [DX1000]
PEEL22LV10AZ [DX0001]
PEEL22LV10AZ@PLCC28 [DX2028]
PEEL22LV10AZ@SOIC24 [DX1033]
PEEL22LV10AZ@TSOP24 [DX1000]
PEEL22LV10AZ+ [DX0001]
PEEL22LV10AZ+@PLCC28 [DX2028]
PEEL22LV10AZ+@SOIC24 [DX1033]
PEEL22LV10AZ+@TSOP24 [DX1000]
PEEL22LV10AZ++ [DX0001]
PEEL22LV10AZ++@PLCC28 [DX2028]
PEEL22LV10AZ++@SOIC24 [DX1033]
PEEL22LV10AZ++@TSOP24 [DX1000]
PEEL253 [DX0001]
PEEL273 [DX0001]

IDT

E(E)PROM/FRAM/NVRAM

IDT5V9885@TQFP32 [DX3001]
IDT5V9885@VFQFPN28 [DX4014]
IDT71024@SOJ32-3 [DX1039]

IGS

E(E)PROM/FRAM/NVRAM

EV29LV160AB [DX0001]
EV29LV160AT [DX0001]
EV29LV640MB [DX0001]
EV29LV640MT [DX0001]

IK Semiconductor

E(E)PROM/FRAM/NVRAM

IK24LC02B [DX0001]
IK24LC02B@SOIC8 [DX1045]
IK24LC04B [DX0001]
IK24LC04B@SOIC8 [DX1045]
IK24LC08B [DX0001]
IK24LC08B@SOIC8 [DX1045]
IK24LC16B [DX0001]
IK24LC16B@SOIC8 [DX1045]

ILITEK

MICROCONTROLLER

M2VQN000@QFP48 [DX3007-8]

IML

E(E)PROM/FRAM/NVRAM

AUO-G1422.2H@TQFN32 [DX4015]
iML1991@QFN32 [DX4015]

MICROCONTROLLER

iML7975@DFN10 [DX4007]
iML7991@QFN32 [DX4015]
iML7991@QFN32(Left Down) [DX4015]
iML8941@QFN40 [DX4017]
iML9921@QFN32 [DX4015]

IMT

E(E)PROM/FRAM/NVRAM

IM29F001B [DX0001]
IM29F001B(REVERSE)@TSOP32 [DX1002]
IM29F001B@PLCC32 [DX2032]
IM29F001B@TSOP32 [DX1002]
IM29F001B@VSOP32 [DX1003]
IM29F001T [DX0001]
IM29F001T(REVERSE)@TSOP32 [DX1002]
IM29F001T@PLCC32 [DX2032]
IM29F001T@TSOP32 [DX1002]

IM29F001T@VSOP32 [DX1003]
IM29F002B [DX0001]
IM29F002B(REVERSE)@TSOP32 [DX1002]
IM29F002B@PLCC32 [DX2032]
IM29F002B@TSOP32 [DX1002]
IM29F002B@VSOP32 [DX1003]
IM29F002T [DX0001]
IM29F002T(REVERSE)@TSOP32 [DX1002]
IM29F002T@PLCC32 [DX2032]
IM29F002T@TSOP32 [DX1002]
IM29F002T@VSOP32 [DX1003]
IM29F004B [DX0001]
IM29F004B(REVERSE)@TSOP32 [DX1002]
IM29F004B@PLCC32 [DX2032]
IM29F004B@TSOP32 [DX1002]
IM29F004B@VSOP32 [DX1003]
IM29F004T [DX0001]
IM29F004T(REVERSE)@TSOP32 [DX1002]
IM29F004T@PLCC32 [DX2032]
IM29F004T@TSOP32 [DX1002]
IM29F004T@VSOP32 [DX1003]
IM29LV004B [DX0001]
IM29LV004B(REVERSE)@TSOP32 [DX1002]
IM29LV004B@PLCC32 [DX2032]
IM29LV004B@TSOP32 [DX1002]
IM29LV004B@VSOP32 [DX1003]
IM29LV004T [DX0001]
IM29LV004T(REVERSE)@TSOP32 [DX1002]
IM29LV004T@PLCC32 [DX2032]
IM29LV004T@TSOP32 [DX1002]
IM29LV004T@VSOP32 [DX1003]
IM29LV400B@PSOP44 [DX1014]
IM29LV400B@TSOP48 [DX1043]
IM29LV400T@PSOP44 [DX1014]
IM29LV400T@TSOP48 [DX1043]

INFINEON

MICROCONTROLLER

PCH7971 [DX1081]
PMA7105@TSSOP38 [DX1012]
SAB-C501G-1E [DX0001]
SAB-C501G-1E@PLCC44 [DX2044]
SAB-C501G-1E@TQFP44 [DX3002]
SAB-C504-2EM@TQFP44 [DX3002]
SAB-C505A-4EM@TQFP44 [DX3002]
SAB-C505CA-4EM@TQFP44 [DX3002]
SAB-C505L-4EM@PQFP80 [DX3018]
SAB-C508-4EM@TQFP64 [DX3014]
SAB-C508-4EP@SDIP64 [DX0064]
SAB-C515C-8EM@TQFP80 [DX3018]
SAB-C540U-1EN@PLCC44 [DX2044]
SAB-C540U-1EP@SDIP52 [DX0052]
SAB-C541U-1EN@PLCC44 [DX2044]
SAB-C541U-1EP@SDIP52 [DX0052]
SAB-XC161CS-32F20F@TQFP144 [DX3035]
SAB-XC161CS-32F40F@TQFP144 [DX3035]
SAB-XC167CI-16F20F@TQFP144 [DX3035]
SAB-XC167CI-16F40F@TQFP144 [DX3035]
SAB-XC167CI-32F20F@TQFP144 [DX3035]
SAB-XC167CI-32F40F@TQFP144 [DX3035]
SAF-C164CI-8EM@TQFP80 [DX3018]
SAF-C501G-1EN@PLCC44 [DX2044]
SAF-C501G-1EP [DX0001]
SAF-C504-2EM@TQFP44 [DX3002]
SAF-C505A-4EM@TQFP44 [DX3002]
SAF-C505CA-4EM@TQFP44 [DX3002]
SAF-C505L-4EM@PQFP80 [DX3018]
SAF-C508-4EM@TQFP64 [DX3014]
SAF-C508-4EP@SDIP64 [DX0064]
SAF-C513AO-2EM@TQFP44 [DX3002]
SAF-C513AO-2EN@PLCC44 [DX2044]
SAF-C513AO-2EP [DX0001]
SAF-C515C-8EM@TQFP80 [DX3018]

SAF-XC161CJ-16F20F@TQFP144 [DX3035]
SAF-XC161CJ-16F40F@TQFP144 [DX3035]
SAF-XC161CS-32F20F@TQFP144 [DX3035]
SAFXC-161CS-32F40F@TQFP144 [DX3035]
SAF-XC164CM-16F20F@TQFP64 [DX3011]
SAF-XC164CM-16F40F@TQFP64 [DX3011]
SAF-XC164CM-4F20F@TQFP64 [DX3011]
SAF-XC164CM-4F40F@TQFP64 [DX3011]
SAF-XC164CM-8F20F@TQFP64 [DX3011]
SAF-XC164CM-8F40F@TQFP64 [DX3011]
SAF-XC164CS-16F20F@TQFP100 [DX3021]
SAF-XC164CS-16F40F@TQFP100 [DX3021]
SAF-XC164CS-32F20F@TQFP100 [DX3021]
SAF-XC164CS-32F40F@TQFP100 [DX3021]
SAF-XC164CS-8F20F@TQFP100 [DX3021]
SAF-XC164CS-8F40F@TQFP100 [DX3021]
SAF-XC164D-16F20F@TQFP100 [DX3021]
SAF-XC164D-16F40F@TQFP100 [DX3021]
SAF-XC164D-8F20F@TQFP100 [DX3021]
SAF-XC164D-8F40F@TQFP100 [DX3021]
SAF-XC164N-16F20F@TQFP100 [DX3021]
SAF-XC164N-16F40F@TQFP100 [DX3021]
SAF-XC164N-8F20F@TQFP100 [DX3021]
SAF-XC164N-8F40F@TQFP100 [DX3021]
SAF-XC164S-16F20F@TQFP100 [DX3021]
SAF-XC164S-16F40F@TQFP100 [DX3021]
SAF-XC164S-8F20F@TQFP100 [DX3021]
SAF-XC164S-8F40F@TQFP100 [DX3021]
SAF-XC167CI-16F20F@TQFP144 [DX3035]
SAF-XC167CI-16F40F@TQFP144 [DX3035]
SAF-XC167CI-32F20F@TQFP144 [DX3035]
SAF-XC167CI-32F40F@TQFP144 [DX3035]
SAF-XC2210U-4FXRTSSOP38 [DX1012]　　SAF-XC2210U-8FXRTSSOP38 [DX1012]
SAF-XC2220L-12FXV@QFN48 [DX4021]　　SAF-XC2220L-20FXV@QFN48 [DX4021]
SAF-XC2220U-4FXV@QFN48 [DX4021]　　SAF-XC2220U-8FXV@QFN48 [DX4021]
SAF-XC2224L-12FXV@QFN48 [DX4021]　　SAF-XC2224L-20FXV@QFN48 [DX4021]
SAF-XC2230L-12F66L@QFP64 [DX3011]
SAF-XC2230L-20F66L@QFP64 [DX3011]
SAF-XC2234L-12F66L@QFP64 [DX3011]
SAF-XC2234L-20F66L@QFP64 [DX3011]
SAF-XC2261N-16F40L@QFP100 [DX3043]
SAF-XC2261N-16F80L@QFP100 [DX3043]
SAF-XC2261N-24F40L@QFP100 [DX3043]
SAF-XC2261N-24F80L@QFP100 [DX3043]
SAF-XC2263M-104F80L@TQFP100 [DX3043]
SAF-XC2263M-56F80L@QFP100 [DX3043]
SAF-XC2263M-72F80L@QFP100 [DX3043]
SAF-XC2263N-16F40L@QFP100 [DX3043]

SAF-XC2263N-16F80L@QFP100 [DX3043]
SAF-XC2263N-24F40L@QFP100 [DX3043]
SAF-XC2263N-24F80L@QFP100 [DX3043]
SAF-XC2263N-40F40L@QFP100 [DX3043]
SAF-XC2263N-40F80L@QFP100 [DX3043]
SAF-XC2264M-104F80L@TQFP100 [DX3043]
SAF-XC2264M-56F80L@QFP100 [DX3043]
SAF-XC2264M-72F80L@QFP100 [DX3043]
SAF-XC2264N-16F40L@QFP100 [DX3043]
SAF-XC2264N-16F80L@QFP100 [DX3043]
SAF-XC2264N-24F40L@QFP100 [DX3043]
SAF-XC2264N-24F80L@QFP100 [DX3043]
SAF-XC2264N-40F40L@QFP100 [DX3043]
SAF-XC2264N-40F80L@QFP100 [DX3043]
SAF-XC2265M-104F80L@TQFP100 [DX3043]
SAF-XC2265M-56F80L@QFP100 [DX3043]
SAF-XC2265M-72F80L@QFP100 [DX3043]
SAF-XC2265N-16F40L@QFP100 [DX3043]
SAF-XC2265N-16F80L@QFP100 [DX3043]
SAF-XC2265N-24F40L@QFP100 [DX3043]
SAF-XC2265N-24F80L@QFP100 [DX3043]
SAF-XC2265N-40F40L@QFP100 [DX3043]
SAF-XC2265N-40F80L@QFP100 [DX3043]
SAF-XC2267M-104F80L@TQFP100 [DX3043]
SAF-XC2267M-56F80L@QFP100 [DX3043]
SAF-XC2267M-72F80L@QFP100 [DX3043]
SAF-XC2268M-104F80L@TQFP100 [DX3043]
SAF-XC2268M-56F80L@QFP100 [DX3043]
SAF-XC2268M-72F80L@QFP100 [DX3043]
SAF-XC2268N-16F40L@QFP100 [DX3043]
SAF-XC2268N-16F80L@QFP100 [DX3043]
SAF-XC2268N-24F40L@QFP100 [DX3043]
SAF-XC2268N-24F80L@QFP100 [DX3043]
SAF-XC2268N-40F40L@QFP100 [DX3043]
SAF-XC2268N-40F80L@QFP100 [DX3043]
SAF-XC2285-72F66L@TQFP144 [DX3035]
SAF-XC2285-96F66L@TQFP144 [DX3035]
SAF-XC2286-72F66L@TQFP144 [DX3035]
SAF-XC2286-96F66L@TQFP144 [DX3035]
SAF-XC2287-72F66L@TQFP144 [DX3035]
SAF-XC2287-96F66L@TQFP144 [DX3035]
SAF-XC2336B-24F66L@QFP64 [DX3011]
SAF-XC2336B-40F66L@QFP64 [DX3011]
SAF-XC2361B-24F80L@QFP100 [DX3043]
SAF-XC2361B-40F80L@QFP100 [DX3043]
SAF-XC2363B-24F80L@QFP100 [DX3043]
SAF-XC2363B-40F80L@QFP100 [DX3043]
SAF-XC2364B-24F80L@QFP100 [DX3043]

SAF-XC2364B-40F80L@QFP100 [DX3043]
SAF-XC2365B-24F80L@QFP100 [DX3043]
SAF-XC2365B-40F80L@QFP100 [DX3043]
SAF-XC2387-72F66L@TQFP144 [DX3035]
SAF-XC2734X-40F80L@QFP64 [DX3011]
SAF-XC2764X-40F80L@QFP100 [DX3043]
SAF-XC822-1FRI@TSSOP16 [DX1000]
SAF-XC822M-1FRI@TSSOP16 [DX1000]
SAF-XC822MT-1FRI@TSSOP16 [DX1000]
SAF-XC822T-0FRI@TSSOP16 [DX1000]
SAF-XC822T-1FRI@TSSOP16 [DX1000]
SAF-XC824M-1FGI@SOIC20 [DX1033]
SAF-XC824MT-1FGI@SOIC20 [DX1033]
SAF-XC835MT-2FGI@SOIC24 [DX1033]
SAF-XC836-2FRI@TSSOP28 [DX1001]
SAF-XC836M-1FRI@TSSOP28 [DX1001]
SAF-XC836M-2FRI@TSSOP28 [DX1001]
SAF-XC836MT-2FRA@TSSOP28 [DX1001]
SAF-XC836MT-2FRI@TSSOP28 [DX1001]
SAF-XC836T-2FRI@TSSOP28 [DX1001]
SAF-XC846-1FR@TSSOP38 [DX1012]
SAF-XC856CLM-13FFI@QFP64 [DX3011]
SAF-XC856CLM-16FFI@QFP64 [DX3011]
SAF-XC856CLM-9FFI@QFP64 [DX3011]
SAF-XC856LM-13FFI@QFP64 [DX3011]
SAF-XC856LM-16FFI@QFP64 [DX3011]
SAF-XC856LM-9FFI@QFP64 [DX3011]
SAF-XC858CA-13FFI(5v)@QFP64 [DX3011]
SAF-XC858CA-16FFI(5v)@QFP64 [DX3011]
SAF-XC858CA-9FFI(5v)@QFP64 [DX3011]
SAF-XC866-1FR@TSSOP38 [DX1012]
SAF-XC866-2FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866-2FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866-4FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866-4FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866L-2FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866L-2FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866L-4FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866L-4FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC878-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878-13FFI(5v)@QFP64 [DX3011]
SAF-XC878-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878-16FFI(5v)@QFP64 [DX3011]
SAF-XC878CM-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878CM-13FFI(5v)@QFP64 [DX3011]
SAF-XC878CM-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878CM-16FFI(5v)@QFP64 [DX3011]
SAF-XC878M-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878M-13FFI(5v)@QFP64 [DX3011]
SAF-XC878M-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878M-16FFI(5v)@QFP64 [DX3011]
SAF-XC886-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886-6FFA(5v)@QFP48 [DX3007]
SAF-XC886-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886-6FFI(5v)@QFP48 [DX3007]
SAF-XC886-8FFA(3.3v)@QFP48 [DX3007]

SAF-XC886-8FFA(5v)@QFP48 [DX3007]
SAF-XC886-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886-8FFI(5v)@QFP48 [DX3007]
SAF-XC886C-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886C-6FFA(5v)@QFP48 [DX3007]
SAF-XC886C-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886C-6FFI(5v)@QFP48 [DX3007]
SAF-XC886C-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886C-8FFA(5v)@QFP48 [DX3007]
SAF-XC886C-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886C-8FFI(5v)@QFP48 [DX3007]
SAF-XC886CLM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886CLM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886CLM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886CLM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-8FFI(5v)@QFP48 [DX3007]
SAF-XC886CM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886CM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886CM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886CM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CM-8FFI(5v)@QFP48 [DX3007]
SAF-XC886LM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886LM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886LM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886LM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886LM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886LM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886LM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886LM-8FFI(5v)@QFP48 [DX3007]
SAF-XC888-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888-6FFA(5v)@QFP64 [DX3011]
SAF-XC888-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888-6FFI(5v)@QFP64 [DX3011]
SAF-XC888-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888-8FFA(5v)@QFP64 [DX3011]
SAF-XC888-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888-8FFI(5v)@QFP64 [DX3011]
SAF-XC888C-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888C-6FFA(5v)@QFP64 [DX3011]
SAF-XC888C-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888C-6FFI(5v)@QFP64 [DX3011]
SAF-XC888C-8FFA(3.3v)@QFP64 [DX3011]

SAF-XC888C-8FFA(5v)@QFP64 [DX3011]
SAF-XC888C-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888C-8FFI(5v)@QFP64 [DX3011]
SAF-XC888CLM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888CLM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888CLM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888CLM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-8FFI(5v)@QFP64 [DX3011]
SAF-XC888CM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888CM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888CM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888CM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CM-8FFI(5v)@QFP64 [DX3011]
SAF-XC888LM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888LM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888LM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888LM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888LM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888LM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888LM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888LM-8FFI(5v)@QFP64 [DX3011]
SAF-XE160FU-4FXR@TSSOP38 [DX1012]
SAF-XE160FU-8FXR@TSSOP38 [DX1012]
SAF-XE161FL-12FXV@QFN48 [DX4021]　　SAF-XE161FL-20FXV@QFN48 [DX4021]
SAF-XE161FU-4FXV@QFN48 [DX4021]　　SAF-XE161FU-8FXV@QFN48 [DX4021]
SAF-XE161HL-12FXV@QFN48 [DX4021]　　SAF-XE161HL-20FXV@QFN48 [DX4021]
SAF-XE162FL-12F66L@QFP64 [DX3011]
SAF-XE162FL-20F66L@QFP64 [DX3011]
SAF-XE162HL-12F66L@QFP64 [DX3011]
SAF-XE162HL-20F66L@QFP64 [DX3011]
SAF-XE164F-24F66L@QFP100 [DX3043]
SAF-XE164F-48F66L@QFP100 [DX3043]
SAF-XE164F-72F66L@QFP100 [DX3043]
SAF-XE164F-96F66L@QFP100 [DX3043]
SAF-XE164FM-24F80L@QFP100 [DX3043]
SAF-XE164FM-48F80L@QFP100 [DX3043]
SAF-XE164FM-72F80L@QFP100 [DX3043]
SAF-XE164FN-24F80L@QFP100 [DX3043]
SAF-XE164FN-40F80L@QFP100 [DX3043]
SAF-XE164G-24F66L@QFP100 [DX3043]
SAF-XE164G-48F66L@QFP100 [DX3043]
SAF-XE164G-72F66L@QFP100 [DX3043]

SAF-XE164G-96F66L@QFP100 [DX3043]
SAF-XE164GM-24F80L@QFP100 [DX3043]
SAF-XE164GM-48F80L@QFP100 [DX3043]
SAF-XE164GM-72F80L@QFP100 [DX3043]
SAF-XE164GN-24F80L@QFP100 [DX3043]
SAF-XE164GN-40F80L@QFP100 [DX3043]
SAF-XE164H-24F66L@QFP100 [DX3043]
SAF-XE164H-48F66L@QFP100 [DX3043]
SAF-XE164H-72F66L@QFP100 [DX3043]
SAF-XE164H-96F66L@QFP100 [DX3043]
SAF-XE164HM-24F80L@QFP100 [DX3043]
SAF-XE164HM-48F80L@QFP100 [DX3043]
SAF-XE164HM-72F80L@QFP100 [DX3043]
SAF-XE164HN-24F80L@QFP100 [DX3043]
SAF-XE164HN-40F80L@QFP100 [DX3043]
SAF-XE164K-24F66L@QFP100 [DX3043]
SAF-XE164K-48F66L@QFP100 [DX3043]
SAF-XE164K-72F66L@QFP100 [DX3043]
SAF-XE164K-96F66L@QFP100 [DX3043]
SAF-XE164KM-24F80L@QFP100 [DX3043]
SAF-XE164KM-48F80L@QFP100 [DX3043]
SAF-XE164KM-72F80L@QFP100 [DX3043]
SAF-XE164KN-24F80L@QFP100 [DX3043]
SAF-XE164KN-40F80L@QFP100 [DX3043]
SAF-XE167F-48F66L@TQFP144 [DX3035]
SAF-XE167F-72F66L@TQFP144 [DX3035]
SAF-XE167F-96F66L@TQFP144 [DX3035]
SAF-XE167G-48F66L@TQFP144 [DX3035]
SAF-XE167G-72F66L@TQFP144 [DX3035]
SAF-XE167G-96F66L@TQFP144 [DX3035]
SAF-XE167H-48F66L@TQFP144 [DX3035]
SAF-XE167H-72F66L@TQFP144 [DX3035]
SAF-XE167H-96F66L@TQFP144 [DX3035]
SAF-XE167K-48F66L@TQFP144 [DX3035]
SAF-XE167K-72F66L@TQFP144 [DX3035]
SAF-XE167K-96F66L@TQFP144 [DX3035]
SAF-XE169FH-136FXL [DX3103]
SAF-XE169FH-200FXL [DX3103]
SAH-C504-2EM@TQFP44 [DX3002]
SAH-C505A-4EM@TQFP44 [DX3002]
SAH-C505CA-4EM@TQFP44 [DX3002]
SAK-C164CI-8EM@TQFP80 [DX3018]
SAK-C504-2EM@TQFP44 [DX3002]
SAK-C505A-4EM@TQFP44 [DX3002]
SAK-C505CA-4EM@TQFP44 [DX3002]
SAK-C505L-4EM@PQFP80 [DX3018]
SAK-C515C-8EM@TQFP80 [DX3018]
SAK-XC161CJ-16F20F@TQFP144 [DX3035]
SAK-XC161CJ-16F40F@TQFP144 [DX3035]
SAK-XC164CM-16F20F@TQFP64 [DX3011]
SAK-XC164CM-16F40F@TQFP64 [DX3011]
SAK-XC164CM-4F20F@TQFP64 [DX3011]
SAK-XC164CM-4F40F@TQFP64 [DX3011]

SAK-XC164CM-8F20F@TQFP64 [DX3011]
SAK-XC164CM-8F40F@TQFP64 [DX3011]
SAK-XC164CS-16F20F@TQFP100 [DX3021]
SAK-XC164CS-16F40F@TQFP100 [DX3021]
SAK-XC164CS-32F20F@TQFP100 [DX3021]
SAK-XC164CS-32F40F@TQFP100 [DX3021]
SAK-XC164CS-8F20F@TQFP100 [DX3021]
SAK-XC164CS-8F40F@TQFP100 [DX3021]
SAK-XC167CI-16F20F@TQFP144 [DX3035]
SAK-XC167CI-16F40F@TQFP144 [DX3035]
SAK-XC2210U-4FXRTSSOP38 [DX1012]
SAK-XC2210U-8FXRTSSOP38 [DX1012]
SAK-XC2220L-12FXV@QFN48 [DX4021]
SAK-XC2220L-20FXV@QFN48 [DX4021]
SAK-XC2220U-4FXV@QFN48 [DX4021]
SAK-XC2220U-8FXV@QFN48 [DX4021]
SAK-XC2224L-12FXV@QFN48 [DX4021]
SAK-XC2224L-20FXV@QFN48 [DX4021]
SAK-XC2230L-12F66L@QFP64 [DX3011]
SAK-XC2230L-20F66L@QFP64 [DX3011]
SAK-XC2234L-12F66L@QFP64 [DX3011]
SAK-XC2234L-20F66L@QFP64 [DX3011]
SAK-XC2261N-16F40L@QFP100 [DX3043]
SAK-XC2261N-16F80L@QFP100 [DX3043]
SAK-XC2261N-24F40L@QFP100 [DX3043]
SAK-XC2261N-24F80L@QFP100 [DX3043]
SAK-XC2263M-104F80L@TQFP100 [DX3043]
SAK-XC2263M-56F80L@QFP100 [DX3043]
SAK-XC2263M-72F80L@QFP100 [DX3043]
SAK-XC2263N-16F40L@QFP100 [DX3043]
SAK-XC2263N-16F80L@QFP100 [DX3043]
SAK-XC2263N-24F40L@QFP100 [DX3043]
SAK-XC2263N-24F80L@QFP100 [DX3043]
SAK-XC2263N-40F40L@QFP100 [DX3043]
SAK-XC2263N-40F80L@QFP100 [DX3043]
SAK-XC2264M-104F80L@TQFP100 [DX3043]
SAK-XC2264M-56F80L@QFP100 [DX3043]
SAK-XC2264M-72F80L@QFP100 [DX3043]
SAK-XC2264N-16F40L@QFP100 [DX3043]
SAK-XC2264N-16F80L@QFP100 [DX3043]
SAK-XC2264N-24F40L@QFP100 [DX3043]
SAK-XC2264N-24F80L@QFP100 [DX3043]
SAK-XC2264N-40F40L@QFP100 [DX3043]
SAK-XC2264N-40F80L@QFP100 [DX3043]
SAK-XC2265M-104F80L@TQFP100 [DX3043]
SAK-XC2265M-56F80L@QFP100 [DX3043]
SAK-XC2265M-72F80L@QFP100 [DX3043]
SAK-XC2265N-16F40L@QFP100 [DX3043]
SAK-XC2265N-16F80L@QFP100 [DX3043]
SAK-XC2265N-24F40L@QFP100 [DX3043]
SAK-XC2265N-24F80L@QFP100 [DX3043]
SAK-XC2265N-40F40L@QFP100 [DX3043]

SAK-XC2265N-40F80L@QFP100 [DX3043]
SAK-XC2267M-104F80L@TQFP100 [DX3043]
SAK-XC2267M-56F80L@QFP100 [DX3043]
SAK-XC2267M-72F80L@QFP100 [DX3043]
SAK-XC2268M-104F80L@TQFP100 [DX3043]
SAK-XC2268M-56F80L@QFP100 [DX3043]
SAK-XC2268M-72F80L@QFP100 [DX3043]
SAK-XC2268N-16F40L@QFP100 [DX3043]
SAK-XC2268N-16F80L@QFP100 [DX3043]
SAK-XC2268N-24F40L@QFP100 [DX3043]
SAK-XC2268N-24F80L@QFP100 [DX3043]
SAK-XC2268N-40F40L@QFP100 [DX3043]
SAK-XC2268N-40F80L@QFP100 [DX3043]
SAK-XC2285-72F66L@TQFP144 [DX3035]
SAK-XC2285-96F66L@TQFP144 [DX3035]
SAK-XC2286-72F66L@TQFP144 [DX3035]
SAK-XC2286-96F66L@TQFP144 [DX3035]
SAK-XC2287-72F66L@TQFP144 [DX3035]
SAK-XC2287-96F66L@TQFP144 [DX3035]
SAK-XC2336B-24F66L@QFP64 [DX3011]
SAK-XC2336B-40F66L@QFP64 [DX3011]
SAK-XC2361B-24F80L@QFP100 [DX3043]
SAK-XC2361B-40F80L@QFP100 [DX3043]
SAK-XC2363B-24F80L@QFP100 [DX3043]
SAK-XC2363B-40F80L@QFP100 [DX3043]
SAK-XC2364B-24F80L@QFP100 [DX3043]
SAK-XC2364B-40F80L@QFP100 [DX3043]
SAK-XC2365B-24F80L@QFP100 [DX3043]
SAK-XC2365B-40F80L@QFP100 [DX3043]
SAK-XC2387-72F66L@TQFP144 [DX3035]
SAK-XC2734X-40F80L@QFP64 [DX3011]
SAK-XC2764X-40F80L@QFP100 [DX3043]
SAK-XC824M-1FGI@SOIC20 [DX1033] SAK-XC846-1FR@TSSOP38 [DX1012]
SAK-XC866-1FR@TSSOP38 [DX1012]
SAK-XC866-2FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866-2FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866-4FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866-4FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866L-2FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866L-2FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866L-4FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866L-4FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC886-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886-6FFA(5v)@QFP48 [DX3007]
SAK-XC886-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886-6FFI(5v)@QFP48 [DX3007]
SAK-XC886-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886-8FFA(5v)@QFP48 [DX3007]

SAK-XC886-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886-8FFI(5v)@QFP48 [DX3007]
SAK-XC886C-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886C-6FFA(5v)@QFP48 [DX3007]
SAK-XC886C-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886C-6FFI(5v)@QFP48 [DX3007]
SAK-XC886C-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886C-8FFA(5v)@QFP48 [DX3007]
SAK-XC886C-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886C-8FFI(5v)@QFP48 [DX3007]
SAK-XC886CLM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886CLM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886CLM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886CLM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-8FFI(5v)@QFP48 [DX3007]
SAK-XC886CM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886CM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886CM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886CM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CM-8FFI(5v)@QFP48 [DX3007]
SAK-XC886LM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886LM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886LM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886LM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886LM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886LM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886LM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886LM-8FFI(5v)@QFP48 [DX3007]
SAK-XC888-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888-6FFA(5v)@QFP64 [DX3011]
SAK-XC888-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888-6FFI(5v)@QFP64 [DX3011]
SAK-XC888-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888-8FFA(5v)@QFP64 [DX3011]
SAK-XC888-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888-8FFI(5v)@QFP64 [DX3011]
SAK-XC888C-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888C-6FFA(5v)@QFP64 [DX3011]
SAK-XC888C-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888C-6FFI(5v)@QFP64 [DX3011]
SAK-XC888C-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888C-8FFA(5v)@QFP64 [DX3011]

SAK-XC888C-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888C-8FFI(5v)@QFP64 [DX3011]
SAK-XC888CLM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888CLM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888CLM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888CLM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-8FFI(5v)@QFP64 [DX3011]
SAK-XC888CM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888CM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888CM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888CM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CM-8FFI(5v)@QFP64 [DX3011]
SAK-XC888LM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888LM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888LM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888LM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888LM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888LM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888LM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888LM-8FFI(5v)@QFP64 [DX3011]
SAK-XE160FU-4FXR@TSSOP38 [DX1012]
SAK-XE160FU-8FXR@TSSOP38 [DX1012]
SAK-XE161FL-12FXV@QFN48 [DX4021]　　SAK-XE161FL-20FXV@QFN48 [DX4021]
SAK-XE161FU-4FXV@QFN48 [DX4021]　　SAK-XE161FU-8FXV@QFN48 [DX4021]
SAK-XE161HL-12FXV@QFN48 [DX4021]　　SAK-XE161HL-20FXV@QFN48 [DX4021]
SAK-XE162FL-12F66L@QFP64 [DX3011]
SAK-XE162FL-20F66L@QFP64 [DX3011]
SAK-XE162HL-12F66L@QFP64 [DX3011]
SAK-XE162HL-20F66L@QFP64 [DX3011]
SAK-XE164FM-24F80L@QFP100 [DX3043]
SAK-XE164FM-48F80L@QFP100 [DX3043]
SAK-XE164FM-72F80L@QFP100 [DX3043]
SAK-XE164FN-24F80L@QFP100 [DX3043]
SAK-XE164FN-40F80L@QFP100 [DX3043]
SAK-XE164GM-24F80L@QFP100 [DX3043]
SAK-XE164GM-48F80L@QFP100 [DX3043]
SAK-XE164GM-72F80L@QFP100 [DX3043]
SAK-XE164GN-24F80L@QFP100 [DX3043]
SAK-XE164GN-40F80L@QFP100 [DX3043]
SAK-XE164HM-24F80L@QFP100 [DX3043]
SAK-XE164HM-48F80L@QFP100 [DX3043]
SAK-XE164HM-72F80L@QFP100 [DX3043]

SAK-XE164HN-24F80L@QFP100 [DX3043]
SAK-XE164HN-40F80L@QFP100 [DX3043]
SAK-XE164KM-24F80L@QFP100 [DX3043]
SAK-XE164KM-48F80L@QFP100 [DX3043]
SAK-XE164KM-72F80L@QFP100 [DX3043]
SAK-XE164KN-24F80L@QFP100 [DX3043]
SAK-XE164KN-40F80L@QFP100 [DX3043]
SAK-XE169FH-136FXL [DX3103]
SAK-XE169FH-200FXL [DX3103]
SAX-XC824M-1FGI@SOIC20 [DX1033]
SAX-XC878-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878-13FFA(5v)@QFP64 [DX3011]
SAX-XC878-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878-16FFA(5v)@QFP64 [DX3011]
SAX-XC878C-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878C-13FFA(5v)@QFP64 [DX3011]
SAX-XC878C-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878C-16FFA(5v)@QFP64 [DX3011]
SAX-XC878CM-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878CM-13FFA(5v)@QFP64 [DX3011]
SAX-XC878CM-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878CM-16FFA(5v)@QFP64 [DX3011]
SAX-XC878L-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878L-13FFA(5v)@QFP64 [DX3011]
SAX-XC878L-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878L-16FFA(5v)@QFP64 [DX3011]
SAX-XC878LM-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878LM-13FFA(5v)@QFP64 [DX3011]
SP30 [DX1081]
SP37 [DX1081]
SP370 [DX1081]
SP373 [DX1081]
TLE4998P3XALA1 [DX0001]
TLE7810G@SOIC28 [DX1033]
XC2234L-20FxL@LQFP64 [DX3011]
XC2330D-12F@LQFP64 [DX3011]
XC2330D-20F@LQFP64 [DX3011]
XC2331D-12F@LQFP64 [DX3011]
XC2331D-20F@LQFP64 [DX3011]
XE160FU-4FxR@TSSOP38 [DX1012-1]
XE160FU-8FxR@TSSOP38 [DX1012-1]
XE162FN-40FxxL@LQFP64 [DX3011]
XE167FM-72FxxL@LQFP144 [DX3035]
XMC1100-T016F0008 [DX1000]
XMC1100-T016F0016 [DX1000]
XMC1100-T016F0064 [DX1000]
XMC1100-T038F0016 [DX1012]
XMC1100-T038F0032 [DX1012]
XMC1100-T038F0064 [DX1012]
XMC1201-T038F0016 [DX1012]
XMC1201-T038F0032 [DX1012]
XMC1201-T038F0064 [DX1012]
XMC1201-T038F0200 [DX1012]
XMC1202-T016X0016 [DX1000]
XMC1202-T016X0032 [DX1000]
XMC1202-T028X0016 [DX1001]
XMC1202-T028X0032 [DX1001]
XMC1301-T016F0008 [DX1000]
XMC1301-T016F0016 [DX1000]
XMC1301-T038F0008 [DX1012]
XMC1301-T038F0016 [DX1012]
XMC1301-T038F0032 [DX1012]
XMC1301-T038F0064 [DX1012]
XMC1302-T038X0016 [DX1012]
XMC1302-T038X0032 [DX1012]
XMC1302-T038X0064 [DX1012]
XMC1302-T038X0200 [DX1012]
XMC4100-F64F128 [DX3011]
XMC4100-F64K128 [DX3011]
XMC4100-Q48F128 [DX4021]

XMC4100-Q48K128 [DX4021]
XMC4104-F64F128 [DX3011]
XMC4104-F64F64 [DX3011]
XMC4104-F64K128 [DX3011]
XMC4104-F64K64 [DX3011]
XMC4104-Q48F128 [DX4021]
XMC4104-Q48F64 [DX4021]
XMC4104-Q48K128 [DX4021]
XMC4104-Q48K64 [DX4021]
XMC4200-F64F256 [DX3011]
XMC4200-F64K256 [DX3011]
XMC4200-Q48F256 [DX4021]
XMC4200-Q48K256 [DX4021]
XMC4400-F100F256 [DX3021]
XMC4400-F100F512 [DX3021]
XMC4400-F100K256 [DX3021]
XMC4400-F100K512 [DX3021]
XMC4400-F64F256 [DX3011]
XMC4400-F64F512 [DX3011]
XMC4400-F64K256 [DX3011]
XMC4400-F64K512 [DX3011]
XMC4402-F100F256 [DX3021]
XMC4402-F100K256 [DX3021]
XMC4402-F64F256 [DX3011]
XMC4402-F64K256 [DX3011]
XMC4500-F100F1024 [DX3021]
XMC4500-F100F768 [DX3021]
XMC4500-F100K1024 [DX3021]
XMC4500-F100K768 [DX3021]
XMC4500-F144F1024 [DX3035]
XMC4500-F144F768 [DX3035]
XMC4500-F144K1024 [DX3035]
XMC4500-F144K768 [DX3035]
XMC4502-F100F768 [DX3021]
XMC4502-F100K768 [DX3021]
XMC4504-F100F512 [DX3021]
XMC4504-F100K512 [DX3021]
XMC4504-F144F512 [DX3035]
XMC4504-F144K512 [DX3035]

INTEGRAL

E(E)PROM/FRAM/NVRAM

IN24AA02A [DX0001]
IN24AA02A@SOIC8 [DX1045]
IN24AA02B [DX0001]
IN24AA02B@SOIC8 [DX1045]
IN24LC02B [DX0001]
IN24LC02B@SOIC8 [DX1045]
IN24LC04B [DX0001]
IN24LC04B@SOIC8 [DX1045]
IN24LC08B [DX0001]
IN24LC08B@SOIC8 [DX1045]
IN24LC16B [DX0001]
IN24LC16B@SOIC8 [DX1045]

INTEL

E(E)PROM/FRAM/NVRAM

27010 [DX0001]
27010@PLCC32 [DX2032]
27010@TSOP32 [DX1002]
27128 [DX0001]
27128A [DX0001]
27128B [DX0001]
2716 [DX0001]
27210 [DX0001]
27256 [DX0001]
2732 [DX0001]
2732A [DX0001]
27512 [DX0001]
2764 [DX0001]
2764A [DX0001]
27C010 [DX0001]
27C010@PLCC32 [DX2032]
27C010@TSOP32 [DX1002]
27C010A [DX0001]
27C010A@PLCC32 [DX2032]
27C010A@TSOP32 [DX1002]

27C020 [DX0001]
27C020@PLCC32 [DX2032]
27C020@TSOP32 [DX1002]
27C040 [DX0001]
27C040@PLCC32 [DX2032]
27C040@TSOP32 [DX1002]
27C100 [DX0001]
27C100@PLCC32 [DX2032]
27C100@TSOP32 [DX1002]
27C128 [DX0001]
27C128@PLCC32 [DX2032]
27C210 [DX0001]
27C210@PLCC44 [DX2044]
27C220 [DX0001]
27C220@PLCC44 [DX2044]
27C240 [DX0001]
27C240@PLCC44 [DX2044]
27C256 [DX0001]
27C256@PLCC32 [DX2032]
27C400 [DX0001]
27C400@PLCC44 [DX2044]
27C512 [DX0001]
27C512@PLCC32 [DX2032]
27C64 [DX0001]
27C64@PLCC32 [DX2032]
27C800 [DX0001]
27S512 [DX0001]
2816A [DX0001]
2817A [DX0001]
2864A [DX0001]
29F64G08CCNE1@TSOP48 [DX1004-3]
68C257 [DX0001]
68C257@PLCC32 [DX2032]
87C256 [DX0001]
87C257 [DX0001]
87C257@PLCC32 [DX2032]
87C64 [DX0001]
CF48F6600M0U0BS@FBGA105 [DX5005]
D27011 [DX0001]
D27513 [DX0001]
D27C011 [DX0001]
D27C513 [DX0001]
D2816 [DX0001]
D28F256 [DX0001]
D28F256A [DX0001]
D28F512 [DX0001]
DA28F016SA@SSOP56 [DX1029]
DA28F016SV@SSOP56 [DX1029]
DA28F320J5@SSOP56 [DX1029]
DA28F320J5A@SSOP56 [DX1029]
DA28F640J5@SSOP56 [DX1029]
DA28F640J5A@SSOP56 [DX1029]
DD28F032SA@TSOP56 [DX1055]
DT28F016SA@SSOP56 [DX1029]
DT28F016SA@TSOP56 [DX1055]
DT28F016SV@SSOP56 [DX1029]
DT28F016SV@TSOP56 [DX1055]
DT28F160F3B@SSOP56 [DX1029]
DT28F160F3T@SSOP56 [DX1029]
DT28F160S3@SSOP56 [DX1029]
DT28F160S5@SSOP56 [DX1029]
DT28F320J5@SSOP56 [DX1029]
DT28F320J5A@SSOP56 [DX1029]
DT28F320S3@SSOP56 [DX1029]
DT28F320S5@SSOP56 [DX1029]
DT28F640J5@SSOP56 [DX1029]
DT28F640J5A@SSOP56 [DX1029]
DT28F800F3B@SSOP56 [DX1029]
DT28F800F3T@SSOP56 [DX1029]
E28F001BX-B@TSOP32 [DX1002]
E28F001BX-T@TSOP32 [DX1002]
E28F002BCT@TSOP40 [DX1006]
E28F002BEB@TSOP40 [DX1006]
E28F002BET@TSOP40 [DX1006]
E28F002BLB@TSOP40 [DX1006]
E28F002BLT@TSOP40 [DX1006]
E28F002BVB@TSOP40 [DX1006]
E28F002BVT@TSOP40 [DX1006]
E28F002BXB@TSOP40 [DX1006]
E28F002BXT@TSOP40 [DX1006]
E28F004B5B@TSOP40 [DX1006]
E28F004B5T@TSOP40 [DX1006]
E28F004BEB@TSOP40 [DX1006]
E28F004BET@TSOP40 [DX1006]
E28F004BLB@TSOP40 [DX1006]
E28F004BLT@TSOP40 [DX1006]
E28F004BVB@TSOP40 [DX1006]
E28F004BVT@TSOP40 [DX1006]
E28F004BXB@TSOP40 [DX1006]
E28F004BXT@TSOP40 [DX1006]
E28F004S3@TSOP40 [DX1006]
E28F004S5@TSOP40 [DX1006]
E28F004SC@TSOP40 [DX1006]
E28F008BEB@TSOP40 [DX1006]
E28F008BET@TSOP40 [DX1006]
E28F008BLB@TSOP40 [DX1006]

E28F008BLT@TSOP40 [DX1006]
E28F008BVB@TSOP40 [DX1006]
E28F008BVT@TSOP40 [DX1006]
E28F008BXB@TSOP40 [DX1006]
E28F008BXT@TSOP40 [DX1006]
E28F008S3@TSOP40 [DX1006]
E28F008S5@TSOP40 [DX1006]
E28F008SA@TSOP40 [DX1006]
E28F008SA-L@TSOP40 [DX1006]
E28F008SC@TSOP40 [DX1006]
E28F010@TSOP32 [DX1002]
E28F016S3@TSOP40 [DX1006]
E28F016S5@TSOP40 [DX1006]
E28F016SA@TSOP56 [DX1055]
E28F016SC@TSOP40 [DX1006]
E28F016SV@TSOP56 [DX1055]
E28F020@TSOP32 [DX1002]
E28F128J3A@TSOP56 [DX1011]
E28F200B5B@TSOP48 [DX1004]
E28F200B5T@TSOP48 [DX1004]
E28F200BVB@TSOP56 [DX1055]
E28F200BVT@TSOP56 [DX1055]
E28F200BXB@TSOP56 [DX1055]
E28F200BXT@TSOP56 [DX1055]
E28F200CVB@TSOP48 [DX1004]
E28F200CVT@TSOP48 [DX1004]
E28F256@TSOP32 [DX1002]
E28F256A@TSOP32 [DX1002]
E28F320J3A@TSOP56 [DX1011]
E28F320J5@TSOP56 [DX1011]
E28F320J5A@TSOP56 [DX1011]
E28F400B5B@TSOP48 [DX1004]
E28F400B5T@TSOP48 [DX1004]
E28F400BLB@TSOP56 [DX1055]
E28F400BLT@TSOP56 [DX1055]
E28F400BVB@TSOP56 [DX1055]
E28F400BVT@TSOP56 [DX1055]
E28F400BXB@TSOP56 [DX1055]
E28F400BXT@TSOP56 [DX1055]
E28F400CVB@TSOP48 [DX1004]
E28F400CVT@TSOP48 [DX1004]
E28F512@TSOP32 [DX1002]
E28F640J3A@TSOP56 [DX1011]
E28F800B5B@TSOP48 [DX1004]
E28F800B5T@TSOP48 [DX1004]
E28F800CEB@TSOP48 [DX1004]
E28F800CET@TSOP48 [DX1004]
E28F800CVB@TSOP48 [DX1004]
E28F800CVT@TSOP48 [DX1004]
E82802AA@TSOP40 [DX1006]
E82802AB@TSOP40 [DX1006]
E82802AC@TSOP40 [DX1006]
F28F008SA@TSOP40(REVERSE) [DX1006]
F28F010@TSOP32 [DX1002]
F28F020@TSOP32 [DX1002]
F28F020@TSOP32(REVERSE) [DX1002]
F28F256@TSOP32 [DX1002]
F28F256A@TSOP32 [DX1002]
F28F512@TSOP32 [DX1002]
G28F640J5@uBGA56 [DX5014]
G28F640J5A@uBGA56 [DX5014]
GE28F008B3BA@uBGA48 [DX5064]
GE28F008B3TA@uBGA48 [DX5064]
GE28F128K18C@FBGA56 [DX5035]
GE28F128K3C@FBGA56 [DX5035]
GE28F128L18B@VFBGA56 [DX5032]
GE28F128L18T@VFBGA56 [DX5032]
GE28F128L30B@VFBGA56 [DX5032]
GE28F128L30T@VFBGA56 [DX5032]
GE28F128W18BC(NO EFP)@VFBGA56 [DX5034]
GE28F128W18BC@VFBGA56 [DX5034]
GE28F128W18BD(NO EFP)@VFBGA56 [DX5035]
GE28F128W18BD@VFBGA56 [DX5035]
GE28F128W18TC(NO EFP)@VFBGA56 [DX5034]
GE28F128W18TC@VFBGA56 [DX5034]
GE28F128W18TD(NO EFP)@VFBGA56 [DX5035]
GE28F128W18TD@VFBGA56 [DX5035]
GE28F128W30BC(NO EFP)@VFBGA56 [DX5034]
GE28F128W30BC@VFBGA56 [DX5034]
GE28F128W30BD(NO EFP)@VFBGA56 [DX5035]
GE28F128W30BD@VFBGA56 [DX5035]
GE28F128W30TC(NO EFP)@VFBGA56 [DX5034]

GE28F128W30TC@VFBGA56 [DX5034]
GE28F128W30TD(NO EFP)@VFBGA56 [DX5035]
GE28F128W30TD@VFBGA56 [DX5035]
GE28F160B3B@uBGA48 [DX5064]
GE28F160B3BC@VFBGA48 [DX5064]
GE28F160B3BD@VFBGA48 [DX5064]
GE28F160B3T@uBGA48 [DX5064]
GE28F160B3TC@VFBGA48 [DX5064]
GE28F160B3TD@VFBGA48 [DX5064]
GE28F160C3BC@VFBGA48 [DX5064]
GE28F160C3BD@VFBGA48 [DX5064]
GE28F160C3TC@VFBGA48 [DX5064]
GE28F160C3TD@VFBGA48 [DX5064]
GE28F256K18C@FBGA79 [DX5036]
GE28F256K3C@FBGA79 [DX5036]
GE28F256L18B@VFBGA79 [DX5164]
GE28F256L18T@VFBGA79 [DX5164]
GE28F256L30B@VFBGA79 [DX5164]
GE28F256L30T@VFBGA79 [DX5164]
GE28F320B3BC@uBGA48 [DX5064]
GE28F320B3BD@uBGA48 [DX5064]
GE28F320B3TC@uBGA48 [DX5064]
GE28F320B3TD@uBGA48 [DX5064]
GE28F320C3BC@VFBGA48 [DX5064]
GE28F320C3BD@VFBGA48 [DX5064]
GE28F320C3TC@VFBGA48 [DX5064]
GE28F320C3TD@VFBGA48 [DX5064]
GE28F320J3A@VFBGA48 [DX5078]
GE28F320J3C@VFBGA48 [DX5078]
GE28F320W18BC(NO EFP)@VFBGA56 [DX5032]
GE28F320W18BC@VFBGA56 [DX5032]
GE28F320W18BD@VFBGA56 [DX5032]
GE28F320W18BE@VFBGA56 [DX5032]
GE28F320W18TC(NO EFP)@VFBGA56 [DX5032]
GE28F320W18TC@VFBGA56 [DX5032]
GE28F320W18TD@VFBGA56 [DX5032]
GE28F320W18TE@VFBGA56 [DX5032]
GE28F320W30BC(NO EFP)@VFBGA56 [DX5032]
GE28F320W30BC@VFBGA56 [DX5032]
GE28F320W30BD(NO EFP)@VFBGA56 [DX5032]
GE28F320W30TC(NO EFP)@VFBGA56 [DX5032]
GE28F320W30TC@VFBGA56 [DX5032]
GE28F320W30TD(NO EFP)@VFBGA56 [DX5032]
GE28F640B3BC@uBGA48 [DX5080]
GE28F640B3TC@uBGA48 [DX5080]
GE28F640C3BC@VFBGA48 [DX5080]
GE28F640C3TC@VFBGA48 [DX5080]
GE28F640J3C@VFBGA48 [DX5078]
GE28F640K18C@FBGA56 [DX5032]
GE28F640K3C@FBGA56 [DX5032]
GE28F640L18B@VFBGA56 [DX5032]
GE28F640L18T@VFBGA56 [DX5032]
GE28F640L30B@VFBGA56 [DX5032]
GE28F640L30T@VFBGA56 [DX5032]
GE28F640W18BC(NO EFP)@uBGA56 [DX5032]
GE28F640W18BC@uBGA56 [DX5032]
GE28F640W18BD@VFBGA56 [DX5032]
GE28F640W18BE@VFBGA56 [DX5032]
GE28F640W18TC(NO EFP)@uBGA56 [DX5032]
GE28F640W18TC@uBGA56 [DX5032]
GE28F640W18TD@VFBGA56 [DX5032]
GE28F640W18TE@VFBGA56 [DX5032]
GE28F640W30BC(NO EFP)@uBGA56 [DX5032]
GE28F640W30BC@uBGA56 [DX5032]
GE28F640W30BD(NO EFP)@uBGA56 [DX5032]
GE28F640W30TC(NO EFP)@uBGA56 [DX5032]
GE28F640W30TC@uBGA56 [DX5032]
GE28F640W30TD(NO EFP)@uBGA56 [DX5032]
GE28F800B3BA@uBGA48 [DX50UN]
GE28F800B3TA@uBGA48 [DX50UN]
GE28F800C3BA@VFBGA48 [DX50UN]
GE28F800C3TA@VFBGA48 [DX50UN]

GT28F016C3BA@FBGA48 [DX5064]
GT28F016C3TA@FBGA48 [DX5064]
GT28F032C3BA@FBGA48 [DX5064]
GT28F032C3TA@FBGA48 [DX5064]
GT28F128W30BC(NO EFP)@uBGA56 [DX5034]
GT28F128W30BC@uBGA56 [DX5034]
GT28F128W30BD(NO EFP)@uBGA56 [DX5035]
GT28F128W30BD@uBGA56 [DX5035]
GT28F128W30TC(NO EFP)@uBGA56 [DX5034]
GT28F128W30TC@uBGA56 [DX5034]
GT28F128W30TD(NO EFP)@uBGA56 [DX5035]
GT28F128W30TD@uBGA56 [DX5035]
GT28F160B3B@uBGA48 [DX5064]
GT28F160B3BA@uBGA48 [DX5064]
GT28F160B3T@uBGA48 [DX5064]
GT28F160B3TA@uBGA48 [DX5064]
GT28F160C3BA@FBGA48 [DX5064]
GT28F160C3TA@FBGA48 [DX5064]
GT28F320B3B@uBGA48 [DX5078]
GT28F320B3BA@uBGA48 [DX5078]
GT28F320B3T@uBGA48 [DX5078]
GT28F320B3TA@uBGA48 [DX5078]
GT28F320C3BA@FBGA48 [DX5078]
GT28F320C3TA@FBGA48 [DX5078]
GT28F800B3B@uBGA48 [DX50UN]
GT28F800B3T@uBGA48 [DX50UN]
JS28F00AM29EWH@TSOP56 [DX1055]
JS28F00AM29EWHS@TSOP56 [DX1055]
JS28F00AM29EWL@TSOP56 [DX1055]
JS28F00AM29EWLS@TSOP56 [DX1055]
JS28F00AP30BF@TSOP56 [DX1011]
JS28F00AP30EF@TSOP56 [DX1011]
JS28F00AP30TF@TSOP56 [DX1011]
JS28F00AP33BF@TSOP56 [DX1011]
JS28F00AP33EF@TSOP56 [DX1011]
JS28F00AP33TF@TSOP56 [DX1011]
JS28F128J3C@TSOP56 [DX1011]
JS28F128J3D@TSOP56 [DX1011]
JS28F128J3F@TSOP56 [DX1011]
JS28F128P30B@TSOP56 [DX1011]
JS28F128P30BF@TSOP56 [DX1011]
JS28F128P30T@TSOP56 [DX1011]
JS28F128P30TF@TSOP56 [DX1011]
JS28F128P33B@TSOP56 [DX1011]
JS28F128P33BF@TSOP56 [DX1011]
JS28F128P33T@TSOP56 [DX1011]
JS28F128P33TF@TSOP56 [DX1011]
JS28F160B3BD@TSOP48 [DX1004]
JS28F160B3TD@TSOP48 [DX1004]
JS28F160C3BD@TSOP48 [DX1004]
JS28F160C3TD@TSOP48 [DX1004]
JS28F256J3C@TSOP56 [DX1011]
JS28F256J3D@TSOP56 [DX1011]
JS28F256J3F@TSOP56 [DX1011]
JS28F256M29EWH@TSOP56 [DX1055]
JS28F256M29EWHS@TSOP56 [DX1055]
JS28F256M29EWL(SD)@TSOP56 [DX1011]
JS28F256M29EWL@TSOP56 [DX1055]
JS28F256M29EWLS@TSOP56 [DX1055]
JS28F256P30B@TSOP56 [DX1011]
JS28F256P30BF@TSOP56 [DX1011]
JS28F256P30T@TSOP56 [DX1011]
JS28F256P30TF@TSOP56 [DX1011]
JS28F256P33B@TSOP56 [DX1011]
JS28F256P33BF@TSOP56 [DX1011]
JS28F256P33T@TSOP56 [DX1011]
JS28F256P33TF@TSOP56 [DX1011]
JS28F320B3BD@TSOP48 [DX1004]
JS28F320B3TD@TSOP48 [DX1004]
JS28F320C3BD@TSOP48 [DX1004]
JS28F320C3TD@TSOP48 [DX1004]
JS28F320J3C@TSOP56 [DX1011]
JS28F320J3D@TSOP56 [DX1011]
JS28F320J3F@TSOP56 [DX1011]
JS28F512M29AWH@FBGA56 [DX1055]
JS28F512M29AWL@FBGA56 [DX1055]
JS28F512M29EWH@TSOP56 [DX1055]
JS28F512M29EWHS@TSOP56 [DX1055]
JS28F512M29EWL@TSOP56 [DX1055]
JS28F512M29EWLS@TSOP56 [DX1055]
JS28F512P30BF@TSOP56 [DX1011]
JS28F512P30EF@TSOP56 [DX1011]
JS28F512P30TF@TSOP56 [DX1011]
JS28F512P33BF@TSOP56 [DX1011]
JS28F512P33EF@TSOP56 [DX1011]
JS28F512P33TF@TSOP56 [DX1011]
JS28F640J3C@TSOP56 [DX1011]

JS28F640J3D@TSOP56 [DX1011]
JS28F640J3F@TSOP56 [DX1011]
JS28F640P30B@TSOP56 [DX1011]
JS28F640P30BF@TSOP56 [DX1011]
JS28F640P30T@TSOP56 [DX1011]
JS28F640P30TF@TSOP56 [DX1011]
JS28F640P33B@TSOP56 [DX1011]
JS28F640P33BF@TSOP56 [DX1011]
JS28F640P33T@TSOP56 [DX1011]
JS28F640P33TF@TSOP56 [DX1011]
JS28F800C3BD@TSOP48 [DX1004]
JS28F800C3TD@TSOP48 [DX1004]
JS29F32G08AAMDB@TSOP48 [DX1004-3]
JS29F32G08FANC1@TSOP48 [DX1004-1]
JS48F4400P0TB00@TSOP56 [DX1011]
JS48F4400P0VB00@TSOP56 [DX1011]
JS48F4400P0VT00@TSOP56 [DX1011]
JZ48F4000L0YBQ0@FBGA88 [DX5001]
JZ48F4000L0YTQ0@FBGA88 [DX5001]
JZ48F4000L0ZBQ0@FBGA88 [DX5001]
JZ48F4000L0ZTQ0@FBGA88 [DX5001]
JZ58F0049M0Y0GE@FBGA128 [DX5087]
JZ58F0049M0Y0GF@FBGA128 [DX5087]
JZ58F0049M0Y0GG@FBGA128 [DX5087]
JZ58F0049M0Y0GH@FBGA128 [DX5087]
JZ58F0070M0Y0KE@FBGA160 [DX5105]
JZ58F0084M0Y1GE@BGA128 [DX5087]
JZ58F0084M0Y1GF@BGA128 [DX5087]
JZ58F0084M0Y1GG@BGA128 [DX5087]
LZ38F4060L0YBB0@FBGA103 [DX5056]
LZ38F4060L0YTB0@FBGA103 [DX5056]
M28F010 [DX0001]
M28F010@PLCC32 [DX2032]
M28F010@TSOP32 [DX1002]
N28F001BN-B@PLCC32 [DX2032]
N28F001BN-T@PLCC32 [DX2032]
N28F001BX-B@PLCC32 [DX2032]
N28F001BX-T@PLCC32 [DX2032]
N28F010@PLCC32 [DX2032]
N28F020@PLCC32 [DX2032]
N28F256@PLCC32 [DX2032]
N28F256A@PLCC32 [DX2032]
N28F512@PLCC32 [DX2032]
N29F040 [DX0001]
N82802AA@PLCC32 [DX2032]
N82802AB@PLCC32 [DX2032]
N82802AC@PLCC32 [DX2032]
NP8P128A13B@FBGA64 [DX5019]
NP8P128A13B@TSOP56 [DX1011]
NP8P128A13T@FBGA64 [DX5019]
NP8P128A13T@TSOP56 [DX1011]
NZ48F4000L0YBQ0@FBGA88 [DX5001]
NZ48F4000L0YTQ0@FBGA88 [DX5001]
NZ48F4000L0ZBQ0@FBGA88 [DX5001]
NZ48F4000L0ZTQ0@FBGA88 [DX5001]
P27011 [DX0001]
P27128A [DX0001]
P27128A@PLCC32 [DX2032]
P27128B [DX0001]
P27128B@PLCC32 [DX2032]
P27256 [DX0001]
P27256@PLCC32 [DX2032]
P27512 [DX0001]
P27513 [DX0001]
P2764A [DX0001]
P2764A@PLCC32 [DX2032]
P27C011 [DX0001]
P27C128 [DX0001]
P27C128@PLCC32 [DX2032]
P27C256 [DX0001]
P27C256@PLCC32 [DX2032]
P27C513 [DX0001]
P27C64 [DX0001]
P27C64@PLCC32 [DX2032]
P28F001BX-B [DX0001]
P28F001BX-T [DX0001]
P28F002BCT [DX0001]
P28F010 [DX0001]
P28F020 [DX0001]
P28F256 [DX0001]
P28F256A [DX0001]
P28F512 [DX0001]
P87C64 [DX0001]
P87C64@PLCC32 [DX2032]
PA28F004S3@PSOP44 [DX1014]
PA28F004S5@PSOP44 [DX1014]
PA28F004SC@PSOP44 [DX1014]
PA28F008S3@PSOP44 [DX1014]
PA28F008S5@PSOP44 [DX1014]
PA28F008SA@PSOP44 [DX1014]
PA28F008SA-L@PSOP44 [DX1014]
PA28F008SC@PSOP44 [DX1014]
PA28F016S3@PSOP44 [DX1014]
PA28F016S5@PSOP44 [DX1014]

PA28F016SC@PSOP44 [DX1014]
PA28F200B5B@PSOP44 [DX1014]
PA28F200B5T@PSOP44 [DX1014]
PA28F200BVB@PSOP44 [DX1014]
PA28F200BVT@PSOP44 [DX1014]
PA28F200BXB@PSOP44 [DX1014]
PA28F200BXT@PSOP44 [DX1014]
PA28F400B5B@PSOP44 [DX1014]
PA28F400B5T@PSOP44 [DX1014]
PA28F400BLB@PSOP44 [DX1014]
PA28F400BLT@PSOP44 [DX1014]
PA28F400BVB@PSOP44 [DX1014]
PA28F400BVT@PSOP44 [DX1014]
PA28F400BXB@PSOP44 [DX1014]
PA28F400BXT@PSOP44 [DX1014]
PA28F800B5B@PSOP44 [DX1014]
PA28F800B5T@PSOP44 [DX1014]
PA28F800BVB@PSOP44 [DX1014]
PA28F800BVT@PSOP44 [DX1014]
PC28F00AG18F@FBGA64 [DX5019]
PC28F00AM29EWH@FBGA64 [DX5074]
PC28F00AM29EWHS@FBGA64 [DX5074]
PC28F00AM29EWL@FBGA64 [DX5074]
PC28F00AM29EWLS@FBGA64 [DX5074]
PC28F00AP30BF@FBGA64 [DX5019]
PC28F00AP30EF@FBGA64 [DX5019]
PC28F00AP30TF@FBGA64 [DX5019]
PC28F00AP33BF@FBGA64 [DX5019]
PC28F00AP33EF@FBGA64 [DX5019]
PC28F00AP33TF@FBGA64 [DX5019]
PC28F128G18F@FBGA64 [DX5019]
PC28F128J3C@FBGA64 [DX5004]
PC28F128J3D@FBGA64 [DX5004]
PC28F128J3F@FBGA64 [DX5004]
PC28F128P30B@EBGA64 [DX5004]
PC28F128P30BF@FBGA64 [DX5004]
PC28F128P30T@EBGA64 [DX5004]
PC28F128P30TF@FBGA64 [DX5004]
PC28F128P33B@EBGA64 [DX5019]
PC28F128P33BF@FBGA64 [DX5019]
PC28F128P33T@EBGA64 [DX5019]
PC28F128P33TF@FBGA64 [DX5019]
PC28F160C3BD@FBGA64 [DX5004]
PC28F160C3TD@FBGA64 [DX5004]
PC28F256G18F@FBGA64 [DX5019]
PC28F256J3C@FBGA64 [DX5020]
PC28F256J3D@FBGA64 [DX5020]
PC28F256J3F@FBGA64 [DX5004]
PC28F256M29EWH@FBGA64 [DX5074]
PC28F256M29EWHS@FBGA64 [DX5074]
PC28F256M29EWL@FBGA64 [DX5074]
PC28F256M29EWLS@FBGA64 [DX5074]
PC28F256P30B@EBGA64 [DX5004]
PC28F256P30BF@FBGA64 [DX5004]
PC28F256P30T@EBGA64 [DX5004]
PC28F256P30TF@FBGA64 [DX5004]
PC28F256P33B@EBGA64 [DX5004]
PC28F256P33BF@FBGA64 [DX5004]
PC28F256P33T@EBGA64 [DX5004]
PC28F256P33TF@FBGA64 [DX5004]
PC28F320B3BC@FBGA64 [DX5004]
PC28F320B3BD@FBGA64 [DX5004]
PC28F320B3TC@FBGA64 [DX5004]
PC28F320B3TD@FBGA64 [DX5004]
PC28F320C3BD@FBGA64 [DX5004]
PC28F320C3TD@FBGA64 [DX5004]
PC28F320J3C@FBGA64 [DX5004]
PC28F320J3D@FBGA64 [DX5004]
PC28F320J3F@FBGA64 [DX5004]
PC28F512G18F@FBGA64 [DX5019]
PC28F512M29AWH@FBGA64 [DX5074]
PC28F512M29AWL@FBGA64 [DX5074]
PC28F512M29EWH@FBGA64 [DX5074]
PC28F512M29EWHS@FBGA64 [DX5074]
PC28F512M29EWL@FBGA64 [DX5074]
PC28F512M29EWLS@FBGA64 [DX5074]
PC28F512P30BF@FBGA64 [DX5019]
PC28F512P30EF@FBGA64 [DX5019]
PC28F512P30TF@FBGA64 [DX5019]
PC28F512P33BF@FBGA64 [DX5019]
PC28F512P33EF@FBGA64 [DX5019]
PC28F512P33TF@FBGA64 [DX5019]
PC28F640J3C@FBGA64 [DX5004]
PC28F640J3D@FBGA64 [DX5004]
PC28F640J3F@FBGA64 [DX5004]
PC28F640P30B@EBGA64 [DX5004]
PC28F640P30BF@EBGA64 [DX5004]
PC28F640P30T@EBGA64 [DX5004]
PC28F640P30TF@EBGA64 [DX5004]
PC28F640P33B@EBGA64 [DX5019]
PC28F640P33BF@EBGA64 [DX5019]
PC28F640P33T@EBGA64 [DX5019]
PC28F640P33TF@EBGA64 [DX5019]
PC28F800C3BD@FBGA64 [DX5004]
PC28F800C3TD@FBGA64 [DX5004]
PC48F3300J0Z00S@FBGA64 [DX5004]

PC48F4400P0TB00@FBGA64 [DX5004]
PC48F4400P0TB0E@FBGA64 [DX5004]
PC48F4400P0VB00@FBGA64 [DX5004]
PC48F4400P0VB0E@FBGA64 [DX5004]
PC48F4400P0VT00@FBGA64 [DX5004]
PF38F1020W0YBQ0@FBGA88 [DX5005]
PF38F1020W0YBQ1@FBGA88 [DX5005]
PF38F1020W0YTQ0@FBGA88 [DX5005]
PF38F1020W0YTQ1@FBGA88 [DX5005]
PF38F1030C0ZBL0@FBGA66 [DX5026]
PF38F1030C0ZTL0@FBGA66 [DX5026]
PF38F1030W0YBQ2@FBGA88 [DX5005]
PF38F1030W0YBQE@FBGA88 [DX5005]
PF38F1030W0YBQF@FBGA88 [DX5005]
PF38F1030W0YCQ3@FBGA88 [DX5005]
PF38F1030W0YCQE@FBGA88 [DX5005]
PF38F1030W0YTQ2@FBGA88 [DX5005]
PF38F1030W0YTQE@FBGA88 [DX5005]
PF38F1030W0YTQF@FBGA88 [DX5005]
PF38F1030W0YUQ3@FBGA88 [DX5005]
PF38F1030W0YUQE(HB)@FBGA88 [DX5005]
PF38F1030W0YUQE@FBGA88 [DX5005]
PF38F1030W0ZBQ0@FBGA88 [DX5005]
PF38F1030W0ZTQ0@FBGA88 [DX5005]
PF38F2020W0ZBQ1@FBGA88 [DX5005]
PF38F2020W0ZTQ1@FBGA88 [DX5005]
PF38F2030W0YBQ1@FBGA88 [DX5005]
PF38F2030W0YBQ2@FBGA88 [DX5005]
PF38F2030W0YBQE@FBGA88 [DX5005]
PF38F2030W0YBQF@FBGA88 [DX5005]
PF38F2030W0YCQ3@FBGA88 [DX5005]
PF38F2030W0YCQE@FBGA88 [DX5005]
PF38F2030W0YTQ1@FBGA88 [DX5005]
PF38F2030W0YTQ2@FBGA88 [DX5005]
PF38F2030W0YTQE@FBGA88 [DX5005]
PF38F2030W0YTQF@FBGA88 [DX5005]
PF38F2030W0YUQ3@FBGA88 [DX5005]
PF38F2030W0YUQE(HB)@FBGA88 [DX5005]
PF38F2030W0YUQE@FBGA88 [DX5005]
PF38F2030W0ZBQ2@FBGA88 [DX5005]
PF38F2030W0ZTQ2@FBGA88 [DX5005]
PF38F2040W0YBQ0@FBGA88 [DX5005]
PF38F2040W0YCQ1@FBGA88 [DX5005]
PF38F2040W0YCQ3@FBGA88 [DX5005]
PF38F2040W0YCQE@FBGA88 [DX5005]
PF38F2040W0YTQ0@FBGA88 [DX5005]
PF38F2040W0YUQ1@FBGA88 [DX5005]
PF38F2040W0YUQ3@FBGA88 [DX5005]
PF38F2040W0YUQE@FBGA88 [DX5005]
PF38F2040W0ZBQ1@FBGA88 [DX5005]
PF38F2040W0ZTQ1@FBGA88 [DX5005]
PF38F3040L0YBQ0@FBGA88 [DX5005]
PF38F3040L0YBQ1@FBGA88 [DX5005]
PF38F3040L0YBQ2@FBGA88 [DX5005]
PF38F3040L0YCQ0@FBGA88 [DX5005]
PF38F3040L0YCQ3@FBGA88 [DX5005]
PF38F3040L0YTQ0@FBGA88 [DX5005]
PF38F3040L0YTQ1@FBGA88 [DX5005]
PF38F3040L0YTQ2@FBGA88 [DX5005]
PF38F3040L0YUQ0@FBGA88 [DX5005]
PF38F3040L0YUQ3@FBGA88 [DX5005]
PF38F3040L0ZBQ0@FBGA88 [DX5005]
PF38F3040L0ZBQ1@FBGA88 [DX5005]
PF38F3040L0ZTQ0@FBGA88 [DX5005]
PF38F3040L0ZTQ1@FBGA88 [DX5005]
PF38F3040M0H0Q0@FBGA88 [DX5005]
PF38F3040M0Y0CE@FBGA107 [DX5077]
PF38F3040M0Y0QE@FBGA88 [DX5005]
PF38F3040M0Y1QE@FBGA88 [DX5005]
PF38F3040M0Y3DE@FBGA56 [DX5094]
PF38F3040M0Y3DF@FBGA56 [DX5094]
PF38F3040M0Y3QE@FBGA88 [DX5005]
PF38F3050L0YBQ1@FBGA88 [DX5005]
PF38F3050L0YBQ2@FBGA88 [DX5005]
PF38F3050L0YCQ0@FBGA88 [DX5005]
PF38F3050L0YCQ2@FBGA88 [DX5005]
PF38F3050L0YCQ3@FBGA88 [DX5005]
PF38F3050L0YTQ1@FBGA88 [DX5005]
PF38F3050L0YTQ2@FBGA88 [DX5005]
PF38F3050L0YUQ0@FBGA88 [DX5005]
PF38F3050L0YUQ2@FBGA88 [DX5005]
PF38F3050L0YUQ3@FBGA88 [DX5005]
PF38F3050L0ZBQ0@FBGA88 [DX5005]
PF38F3050L0ZBQ1@FBGA88 [DX5005]
PF38F3050L0ZTQ0@FBGA88 [DX5005]
PF38F3050L0ZTQ1@FBGA88 [DX5005]
PF38F3050M0Y0CE@FBGA107 [DX5077]
PF38F3050M0Y0CF@FBGA107 [DX5077]
PF38F3050M0Y0QE@FBGA88 [DX5005]
PF38F3050M0Y0QF@FBGA88 [DX5005]
PF38F3050M0Y0YE@FBGA84 [DX5079]
PF38F3050M0Y3DE@FBGA56 [DX5094]
PF38F3050M0Y3DF@FBGA56 [DX5094]
PF38F3050M0Y3DG@FBGA56 [DX5094]

PF38F3050M0Y3DH@FBGA56 [DX5094]
PF38F3050M0Y3DM@FBGA56 [DX5183]
PF38F3050M0Y3QE@FBGA88 [DX5005]
PF38F3050M0Y3QF@FBGA88 [DX5005]
PF38F3060M0Y0CE@FBGA107 [DX5077]
PF38F3060M0Y1EE@FBGA132 [DX5069]
PF38F3060M0Y1EF@FBGA132 [DX5069]
PF38F3060M0Y1EG@FBGA132 [DX5069]
PF38F3060M0Y1EM@FBGA132 [DX5069]
PF38F3350LLZDQ0@FBGA88 [DX5005]
PF38F3350WWZDQ0@FBGA88 [DX5005]
PF38F3350WWZDQ1@FBGA88 [DX5005]
PF38F4040L0YCQ0@FBGA88 [DX5001]
PF38F4040L0YUQ0@FBGA88 [DX5001]
PF38F4050L0YAQE@FBGA88 [DX5005]
PF38F4050L0YBQ0@FBGA88 [DX5001]
PF38F4050L0YBQ1@FBGA88 [DX5001]
PF38F4050L0YBQ2@FBGA88 [DX5001]
PF38F4050L0YCQ0@FBGA88 [DX5001]
PF38F4050L0YCQ3@FBGA88 [DX5001]
PF38F4050L0YCQ4@FBGA88 [DX5001]
PF38F4050L0YTQ0@FBGA88 [DX5001]
PF38F4050L0YTQ1@FBGA88 [DX5001]
PF38F4050L0YTQ2@FBGA88 [DX5001]
PF38F4050L0YUQ0@FBGA88 [DX5001]
PF38F4050L0YUQ3@FBGA88 [DX5001]
PF38F4050L0YUQ4@FBGA88 [DX5001]
PF38F4050L0YWQE@FBGA88 [DX5005]
PF38F4050L0ZBQ0@FBGA88 [DX5001]
PF38F4050L0ZBQ1@FBGA88 [DX5001]
PF38F4050L0ZTQ0@FBGA88 [DX5001]
PF38F4050L0ZTQ1(HB)@FBGA88 [DX5001]
PF38F4050L0ZTQ1@FBGA88 [DX5001]
PF38F4050M0Y0C0@FBGA107 [DX5077]
PF38F4050M0Y0CG@FBGA107 [DX5077]
PF38F4050M0Y0Q0@FBGA88 [DX5005]
PF38F4050M0Y0YE@FBGA84 [DX5079]
PF38F4050M0Y1Q0@FBGA88 [DX5005]
PF38F4050M0Y3CE@FBGA107 [DX5077]
PF38F4050M0Y3DE@FBGA56 [DX5114]
PF38F4050M0Y3DF@FBGA56 [DX5094]
PF38F4050M0YEQ0@FBGA88 [DX5005]
PF38F4050M0YEQF@FBGA88 [DX5005]
PF38F4055L0YBQ2@FBGA88 [DX5001]
PF38F4055L0YTQ2@FBGA88 [DX5001]
PF38F4060L0YBB0@FBGA103 [DX5005]
PF38F4060L0YBB1@FBGA103 [DX5056]
PF38F4060L0YTB0@FBGA103 [DX5056]
PF38F4060L0YTB1@FBGA103 [DX5056]
PF38F4060M0Y0BE@FBGA105 [DX5056]
PF38F4060M0Y0C0@FBGA107 [DX5077]
PF38F4060M0Y0CE@FBGA107 [DX5077]
PF38F4060M0Y0YE@FBGA84 [DX5079]
PF38F4060M0Y3CE@FBGA107 [DX5077]
PF38F4060M0Y3DE@FBGA56 [DX5114]
PF38F4060M0Y3DF@FBGA56 [DX5114]
PF38F4060M0Y3DG@FBGA56 [DX5114]
PF38F4060M0Y3DH@FBGA56 [DX5114]
PF38F4060M0Y3DM@FBGA56 [DX5183]
PF38F4060M0Y3DN@FBGA56 [DX5183]
PF38F4350LLYBQ1@FBGA88 [DX5001]
PF38F4350LLYBQ2@FBGA88 [DX5001]
PF38F4350LLYTQ1@FBGA88 [DX5001]
PF38F4350LLYTQ2@FBGA88 [DX5001]
PF38F4450LLYBQ0@FBGA88 [DX5001]
PF38F4450LLYBQ2@FBGA88 [DX5001]
PF38F4450LLYTQ0@FBGA88 [DX5001]
PF38F4450LLYTQ2@FBGA88 [DX5001]
PF38F4450LVYBQ0@FBGA88 [DX5001]
PF38F4450LVYBQ2@FBGA88 [DX5001]
PF38F4450LVYTQ0@FBGA88 [DX5001]
PF38F4450LVYTQ2@FBGA88 [DX5001]
PF38F4455LLYBQ0@FBGA88 [DX50UN]
PF38F4455LLYBQ1@FBGA88 [DX50UN]
PF38F4455LLYBQ2@FBGA88 [DX50UN]
PF38F4455LLYTQ0@FBGA88 [DX50UN]
PF38F4455LLYTQ1@FBGA88 [DX50UN]
PF38F4455LLYTQ2@FBGA88 [DX50UN]
PF38F4460EEYBQ0@FBGA88 [DX5001]
PF38F4460EEYTQ0@FBGA88 [DX5001]
PF38F4460LLYBB0@FBGA103 [DX5056]
PF38F4462LLYDB0@FBGA103 [DX5056]
PF38F4466LVYBQ0@FBGA88 [DX50UN]
PF38F4466LVYTQ0@FBGA88 [DX50UN]
PF38F4470LLYBB0@FBGA103 [DX5056]
PF38F5050M0Y0C0@FBGA107 [DX5077]
PF38F5050M0Y0CE@FBGA107 [DX5077]
PF38F5060M0Y0B0@FBGA105 [DX5056]
PF38F5060M0Y0BE@FBGA105 [DX5056]
PF38F5060M0Y0C0(Inv)@FBGA107 [DX5077]
PF38F5060M0Y0C0@FBGA107 [DX5077]
PF38F5060M0Y0CE@FBGA107 [DX5077]

PF38F5060M0Y0CF@FBGA107 [DX5077]
PF38F5060M0Y0CH@FBGA107 [DX5077]
PF38F5060M0Y0CJ@FBGA107 [DX5077]
PF38F5060M0Y1EE@FBGA132 [DX5069]
PF38F5060M0Y3CE@FBGA107 [DX5077]
PF38F5060M0Y3DE@FBGA56 [DX5134]
PF38F5060M0Y3DF@FBGA56 [DX5114]
PF38F5060M0Y3DG@FBGA56 [DX5114]
PF38F5060M0Y3DH@FBGA56 [DX5114]
PF38F5060M0Y3DJ@FBGA56 [DX5114]
PF38F5060M0Y3DK@FBGA56 [DX5114]
PF38F5066M0Y3DE@FBGA56 [DX5114]
PF38F5070M0Y0B0@FBGA105 [DX5056]
PF38F5070M0Y0BE@FBGA105 [DX5056]
PF38F5070M0Y0CE@FBGA107 [DX5056]
PF38F5070M0Y0V0@FBGA165 [DX5111]
PF38F5070M0Y0VE@FBGA165 [DX5111]
PF38F5070M0Y1EE@FBGA132 [DX5069]
PF38F5070M0Y1V0@FBGA165 [DX5111]
PF38F5070M0Y1VE(HB)@FBGA165 [DX5111]
PF38F5070M0Y1VE@FBGA165 [DX5111]
PF38F5070M0Y3CE@FBGA107 [DX5056]
PF38F5070M0Y3CF@FBGA107 [DX5056]
PF38F5070M0Y3DE@FBGA56 [DX5134]
PF38F5080M0Y0B0@FBGA105 [DX5056]
PF38F5566MMY0C0@FBGA107 [DX5077]
PF38F6070M0H0Q0@FBGA88 [DX5005]
PF38F6070M0Y0B0@FBGA105 [DX5056]
PF38F6070M0Y0BE@FBGA105 [DX5056]
PF38F6070M0Y0VE@FBGA165 [DX5120]
PF38F6070M0Y0VF@FBGA165 [DX5120]
PF38F6070M0Y1CE@FBGA107 [DX50UN]
PF38F6070M0Y1VF@FBGA165 [DX50UN]
PF38F6080M0Y0VE@FBGA165 [DX5121]
PF38F6080M0Y1VE@FBGA165 [DX50UN]
PF48F2000P0XBQ0@FBGA88 [DX5005]
PF48F2000P0XTQ0@FBGA88 [DX5005]
PF48F2000P0ZBQ0@FBGA88 [DX5005]
PF48F2000P0ZTQ0@FBGA88 [DX5005]
PF48F3000L0YBQ0@FBGA88 [DX5005]
PF48F3000L0YTQ0@FBGA88 [DX5005]
PF48F3000L0ZBQ0@FBGA88 [DX5005]
PF48F3000L0ZTQ0@FBGA88 [DX5005]
PF48F3000M0Y0QE@FBGA88 [DX5005]
PF48F3000M0Y1QE@FBGA88 [DX5005]
PF48F3000P0XBQ0@FBGA88 [DX5005]
PF48F3000P0XTQ0@FBGA88 [DX5005]
PF48F3000P0ZBQ0@FBGA88 [DX5005]
PF48F3000P0ZBQE@FBGA88 [DX5005]
PF48F3000P0ZTQ0@FBGA88 [DX5005]
PF48F3000P0ZTQE@FBGA88 [DX5005]
PF48F3000W0YBQ0@FBGA88 [DX5005]
PF48F3000W0YTQ0@FBGA88 [DX5005]
PF48F3000W0ZBQ0@FBGA88 [DX5005]
PF48F3000W0ZTQ0@FBGA88 [DX5005]
PF48F3300W0YBQ0@FBGA88 [DX5005]
PF48F3300W0YDQ0@FBGA88 [DX5005]
PF48F3300W0YTQ0@FBGA88 [DX5005]
PF48F4000L0YBQ0@FBGA88 [DX5001]
PF48F4000L0YTB0@FBGA103 [DX5056]
PF48F4000L0YTQ0@FBGA88 [DX5001]
PF48F4000M0Y0CE@FBGA107 [DX5077]
PF48F4000P0XBQ0@FBGA88 [DX5001]
PF48F4000P0XTQ0@FBGA88 [DX5001]
PF48F4000P0ZBQ0@FBGA88 [DX5001]
PF48F4000P0ZBQE@FBGA88 [DX5001]
PF48F4000P0ZTQ0@FBGA88 [DX5001]
PF48F4000P0ZTQE@FBGA88 [DX5001]
PF48F4040LVYBQ0(BEEP)@FBGA88 [DX5001]
PF48F4040LVYBQ0(BP)@FBGA88 [DX5001]
PF48F4040LVYTQ0(BEEP)@FBGA88 [DX5001]
PF48F4040LVYTQ0(BP)@FBGA88 [DX5001]
PF48F4400L0YDQ0@FBGA88 [DX5001]
PF48F4400L0ZDQ0@FBGA88 [DX5001]
PF48F4400P0TBQ0@FBGA88 [DX5001]
PF48F4400P0VBQ0@FBGA88 [DX5001]
PF48F4400P0VBQE@FBGA88 [DX5001]
PF48F4400P0VTQ0@FBGA88 [DX5001]
PF48F5000M0Y0B0@FBGA105 [DX5077]
PF48F5000M0Y0BE@FBGA105 [DX5077]
PF48F5000M0Y0C0@FBGA107 [DX5077]
PF48F5000M0Y1B0@FBGA105 [DX5077]
PF48F5000M0Y1BE@FBGA105 [DX5077]
PF48F5500M0Y0B0@FBGA105 [DX5077]
PF48F6000M0Y0BE@FBGA105 [DX5077]
PF48F6000M0Y0BF@FBGA105 [DX5077]
PF48F6000M0Y0BG@FBGA105 [DX5077]
PF48F6000M0Y0BH@FBGA105 [DX5077]
PF48F6000M0Y1BE@FBGA105 [DX5077]
PF48F6600M0U0BE@FBGA105 [DX5005]

PF48F6600M0U0BF@FBGA105 [DX5005]
PF58F0026M0Y1BE@FBGA105 [DX5056]
PF58F0042M0Y0WE@FBGA165 [DX5101]
PF58F0048M0Y0WE@FBGA165 [DX5101]
PF58F0051M0Y1WE@FBGA165 [DX5109]
PF58F0051M0Y1WF@FBGA165 [DX5109]
PF58F0051M0Y1WG@FBGA165 [DX5109]
PF58F0051M0Y1WH@FBGA165 [DX5108]
PF58F0051M0Y1WJ@FBGA165 [DX5108]
PF58F0051M0Y1WK@FBGA165 [DX5108]
PF58F0058M0Y1WE@FBGA165 [DX5108]
PF58F0062M0Y1BF@FBGA105 [DX5056]
PF58F0062M0Y1BG@FBGA105 [DX5056]
PF58F0067M0Y0WE@FBGA165 [DX50UN]
PF58F0067M0Y0WF@FBGA165 [DX5101]
PF58F0068M0Y0WE@FBGA165 [DX5101]
PF58F0071M0Y0WE@FBGA165 [DX5101]
PF58F0073M0Y1WE@FBGA165 [DX5108]
PF58F0075M0Y1WE@FBGA165 [DX5108]
PH28F128L18B@VFBGA56 [DX5032]
PH28F128L18T@VFBGA56 [DX5032]
PH28F128L30B@VFBGA56 [DX5032]
PH28F128L30T@VFBGA56 [DX5032]
PH28F128W18BC(NO EFP)@VFBGA56 [DX5034]
PH28F128W18BC@VFBGA56 [DX5034]
PH28F128W18BD(NO EFP)@VFBGA56 [DX5035]
PH28F128W18BD@VFBGA56 [DX5035]
PH28F128W18TC(NO EFP)@VFBGA56 [DX5034]
PH28F128W18TC@VFBGA56 [DX5034]
PH28F128W18TD(NO EFP)@VFBGA56 [DX5035]
PH28F128W18TD@VFBGA56 [DX5035]
PH28F160B3BD@uBGA48 [DX5064]
PH28F160B3TD@uBGA48 [DX5064]
PH28F160C3BD@VFBGA48 [DX5064]
PH28F160C3TD@VFBGA48 [DX5064]
PH28F256L18B@VFBGA79 [DX5164]
PH28F256L18T@VFBGA79 [DX5164]
PH28F256L30B@VFBGA79 [DX5164]
PH28F256L30T@VFBGA79 [DX5164]
PH28F320B3BD@uBGA48 [DX5064]
PH28F320B3TD@uBGA48 [DX5064]
PH28F320C3BD@VFBGA48 [DX5064]
PH28F320C3TD@VFBGA48 [DX5064]
PH28F320W18BD@VFBGA56 [DX5032]
PH28F320W18BE@VFBGA56 [DX5032]
PH28F320W18TD@VFBGA56 [DX5032]
PH28F320W18TE@VFBGA56 [DX5032]
PH28F320W30BD@VFBGA56 [DX5032]
PH28F320W30TD@VFBGA56 [DX5032]
PH28F640C3BC@VFBGA48 [DX5080]
PH28F640C3TC@VFBGA48 [DX5080]
PH28F640L18B@VFBGA56 [DX5032]
PH28F640L18T@VFBGA56 [DX5032]
PH28F640L30B@VFBGA56 [DX5032]
PH28F640L30T@VFBGA56 [DX5032]
PH28F640W18BD@VFBGA56 [DX5032]
PH28F640W18BE@VFBGA56 [DX5032]
PH28F640W18TD@VFBGA56 [DX5032]
PH28F640W18TE@VFBGA56 [DX5032]
PH28F640W30BD@VFBGA56 [DX5032]
PH28F640W30TD@VFBGA56 [DX5032]
QB25F016S33B60@SOIC8 [DX1044#1]
QB25F016S33T60@SOIC8 [DX1044#1]
QB25F160S33B60@SOIC16 [DX1033#1]
QB25F160S33T60@SOIC16 [DX1033#1]
QB25F320S33B60@SOIC16 [DX1033#1]
QB25F320S33T60@SOIC16 [DX1033#1]
QB25F640S33B60@SOIC16 [DX1033#1]
QB25F640S33T60@SOIC16 [DX1033#1]
QH25F016S33B60@SOIC8 [DX1044#1]
QH25F016S33T60@SOIC8 [DX1044#1]
QH25F160S33B60@SOIC16 [DX1033#1]
QH25F160S33T60@SOIC16 [DX1033#1]
QH25F320S33B60@SOIC16 [DX1033#1]
QH25F320S33T60@SOIC16 [DX1033#1]
QH25F640S33B60@SOIC16 [DX1033#1]
QH25F640S33T60@SOIC16 [DX1033#1]
RC28F128J3A@FBGA64 [DX5004]
RC28F128J3C@FBGA64 [DX5004]
RC28F128J3D@FBGA64 [DX5004]
RC28F128J3F@FBGA64 [DX5004]
RC28F128K18C@FBGA64 [DX5004]
RC28F128K3C@FBGA64 [DX5004]
RC28F128P30B@EBGA64 [DX5004]
RC28F128P30BF@FBGA64 [DX5004]
RC28F128P30T@EBGA64 [DX5004]
RC28F128P30TF@FBGA64 [DX5004]
RC28F128P33B@EBGA64 [DX5019]

RC28F128P33BF@FBGA64 [DX5019]
RC28F128P33T@EBGA64 [DX5019]
RC28F128P33TF@FBGA64 [DX5019]
RC28F160C3BA@FBGA64 [DX5004]
RC28F160C3BC@FBGA64 [DX5004]
RC28F160C3BD@FBGA64 [DX5004]
RC28F160C3TA@FBGA64 [DX5004]
RC28F160C3TC@FBGA64 [DX5004]
RC28F160C3TD@FBGA64 [DX5004]
RC28F256J3C@FBGA64 [DX5020]
RC28F256J3D@FBGA64 [DX5020]
RC28F256J3F@FBGA64 [DX5004]
RC28F256K18C@FBGA64 [DX5020]
RC28F256K3C@FBGA64 [DX5020]
RC28F256M29EWH@FBGA64 [DX5074]
RC28F256M29EWHS@FBGA64 [DX5074]
RC28F256M29EWL@FBGA64 [DX5074]
RC28F256M29EWLS@FBGA64 [DX5074]
RC28F256P30B@EBGA64 [DX5004]
RC28F256P30BF@FBGA64 [DX5004]
RC28F256P30T@EBGA64 [DX5004]
RC28F256P30TF@FBGA64 [DX5004]
RC28F256P33B@EBGA64 [DX5004]
RC28F256P33BF@FBGA64 [DX5004]
RC28F256P33T@EBGA64 [DX5004]
RC28F256P33TF@FBGA64 [DX5004]
RC28F320B3BC@FBGA64 [DX5004]
RC28F320B3BD@FBGA64 [DX5004]
RC28F320B3TC@FBGA64 [DX5004]
RC28F320B3TD@FBGA64 [DX5004]
RC28F320C3BA@FBGA64 [DX5004]
RC28F320C3BC@FBGA64 [DX5004]
RC28F320C3BD@FBGA64 [DX5004]
RC28F320C3TA@FBGA64 [DX5004]
RC28F320C3TC@FBGA64 [DX5004]
RC28F320C3TD@FBGA64 [DX5004]
RC28F320J3A@FBGA64 [DX5004]
RC28F320J3C@FBGA64 [DX5004]
RC28F320J3D@FBGA64 [DX5004]
RC28F320J3F@FBGA64 [DX5004]
RC28F512M29EWH@FBGA64 [DX5074]
RC28F512M29EWHS@FBGA64 [DX5074]
RC28F512M29EWL@FBGA64 [DX5074]
RC28F512M29EWLS@FBGA64 [DX5074]
RC28F640C3BC@FBGA64 [DX5004]
RC28F640C3TC@FBGA64 [DX5004]
RC28F640J3A@FBGA64 [DX5004]
RC28F640J3C@FBGA64 [DX5004]
RC28F640J3D@FBGA64 [DX5004]
RC28F640J3F@FBGA64 [DX5004]
RC28F640K18C@FBGA64 [DX5004]
RC28F640K3C@FBGA64 [DX5004]
RC28F640P30B@EBGA64 [DX5004]
RC28F640P30BF@EBGA64 [DX5004]
RC28F640P30T@EBGA64 [DX5004]
RC28F640P30TF@EBGA64 [DX5004]
RC28F640P33B@EBGA64 [DX5019]
RC28F640P33BF@EBGA64 [DX5019]
RC28F640P33T@EBGA64 [DX5019]
RC28F640P33TF@EBGA64 [DX5019]
RC28F800C3BA@FBGA64 [DX5004]
RC28F800C3BD@FBGA64 [DX5004]
RC28F800C3TA@FBGA64 [DX5004]
RC28F800C3TD@FBGA64 [DX5004]
RC48F3300J0Z00S@FBGA64 [DX5004]
RC48F4400P0TB00@FBGA64 [DX5004]
RC48F4400P0TB0E@FBGA64 [DX5004]
RC48F4400P0VB00@FBGA64 [DX5004]
RC48F4400P0VB0E@FBGA64 [DX5004]
RC48F4400P0VT00@FBGA64 [DX5004]
RD28F1602C3B@FBGA66 [DX5005]
RD28F1602C3B70@FBGA66 [DX5005]
RD28F1602C3BD@FBGA66 [DX5005]
RD28F1602C3T@FBGA66 [DX5005]
RD28F1602C3T70@FBGA66 [DX5005]
RD28F1602C3TD@FBGA66 [DX5005]
RD28F1604C3B@FBGA66 [DX5026]
RD28F1604C3BD@FBGA66 [DX5026]
RD28F1604C3T@FBGA66 [DX5026]
RD28F1604C3TD@FBGA66 [DX5026]
RD28F3204C3B@FBGA66 [DX5026]
RD28F3204C3T@FBGA66 [DX5026]
RD28F3204W18B(NO EFP)@FBGA96 [DX5051]
RD28F3204W18B@FBGA96 [DX5051]
RD28F3204W18T(NO EFP)@FBGA96 [DX5051]
RD28F3204W18T@FBGA96 [DX5051]
RD28F3204W30B(NO EFP)@FBGA96 [DX5051]
RD28F3204W30B@FBGA96 [DX5051]
RD28F3204W30T(NO EFP)@FBGA96 [DX5051]

RD28F3204W30T@FBGA96 [DX5051]
RD28F3208C3B@FBGA66 [DX5051]
RD28F3208C3T@FBGA66 [DX5051]
RD28F3208W30B(NO EFP)@FBGA96 [DX5051]
RD28F3208W30B@FBGA96 [DX5051]
RD28F3208W30T(NO EFP)@FBGA96 [DX5051]
RD28F3208W30T@FBGA96 [DX5051]
RD28F6408W18B(NO EFP)@FBGA96 [DX5051]
RD28F6408W18B@FBGA96 [DX5051]
RD28F6408W18T(NO EFP)@FBGA96 [DX5051]
RD28F6408W18T@FBGA96 [DX5051]
RD28F6408W30B(NO EFP)@FBGA96 [DX5051]
RD28F6408W30B@FBGA96 [DX5051]
RD28F6408W30T(NO EFP)@FBGA96 [DX5051]
RD28F6408W30T@FBGA96 [DX5051]
RD38F1010C0ZB@FBGA66 [DX5026]
RD38F1010C0ZBL0@FBGA66 [DX5026]
RD38F1010C0ZT@FBGA66 [DX5026]
RD38F1010C0ZTL0@FBGA66 [DX5026]
RD38F1010W0YTL0@FBGA67 [DX5005]
RD38F1020C0ZB@FBGA66 [DX5026]
RD38F1020C0ZT@FBGA66 [DX5026]
RD38F1020W0YBQ0@FBGA88 [DX5005]
RD38F1020W0YBQ1@FBGA88 [DX5005]
RD38F1020W0YTQ0@FBGA88 [DX5005]
RD38F1020W0YTQ1@FBGA88 [DX5005]
RD38F1030W0YBQ2@FBGA88 [DX5005]
RD38F1030W0YTQ2@FBGA88 [DX5005]
RD38F1030W0ZBQ0@FBGA88 [DX5005]
RD38F1030W0ZTQ0@FBGA88 [DX5005]
RD38F2010W0YBQ0@FBGA88 [DX5005]
RD38F2010W0YTQ0@FBGA88 [DX5005]
RD38F2010W0ZBQ0@FBGA88 [DX5005]
RD38F2010W0ZTQ0@FBGA88 [DX5005]
RD38F2020W0YBQ0@FBGA88 [DX5005]
RD38F2020W0YTQ0@FBGA88 [DX5005]
RD38F2020W0ZBQ0@FBGA88 [DX5005]
RD38F2020W0ZBQ1@FBGA88 [DX5005]
RD38F2020W0ZTQ0@FBGA88 [DX5005]
RD38F2020W0ZTQ1@FBGA88 [DX5005]
RD38F2030W0YBQ0@FBGA88 [DX5005]
RD38F2030W0YBQ1@FBGA88 [DX5005]
RD38F2030W0YBQ2@FBGA88 [DX5005]
RD38F2030W0YBQE@FBGA88 [DX5005]
RD38F2030W0YBQF@FBGA88 [DX5005]
RD38F2030W0YTQ0@FBGA88 [DX5005]
RD38F2030W0YTQ1@FBGA88 [DX5005]
RD38F2030W0YTQ2@FBGA88 [DX5005]
RD38F2030W0YTQE@FBGA88 [DX5005]
RD38F2030W0YTQF@FBGA88 [DX5005]
RD38F2030W0ZBQ0@FBGA88 [DX5005]
RD38F2030W0ZBQ1@FBGA88 [DX5005]
RD38F2030W0ZBQ2@FBGA88 [DX5005]
RD38F2030W0ZTQ0@FBGA88 [DX5005]
RD38F2030W0ZTQ1@FBGA88 [DX5005]
RD38F2030W0ZTQ2@FBGA88 [DX5005]
RD38F2040W0YBQ0@FBGA88 [DX5005]
RD38F2040W0YBQ1@FBGA88 [DX5005]
RD38F2040W0YTQ0@FBGA88 [DX5005]
RD38F2040W0YTQ1@FBGA88 [DX5005]
RD38F2040W0ZBQ0@FBGA88 [DX5005]
RD38F2040W0ZBQ1@FBGA88 [DX5005]
RD38F2040W0ZTQ0@FBGA88 [DX5005]
RD38F2040W0ZTQ1@FBGA88 [DX5005]
RD38F2220WWYBQ0@FBGA88 [DX5005]
RD38F2220WWYDQ0@FBGA88 [DX5005]
RD38F2220WWYTQ0@FBGA88 [DX5005]
RD38F2220WWZBQ0@FBGA88 [DX5005]
RD38F2220WWZDQ0@FBGA88 [DX5005]
RD38F2220WWZTQ0@FBGA88 [DX5005]
RD38F2230WWYBQ0@FBGA88 [DX5005]
RD38F2230WWYDQ0@FBGA88 [DX5005]
RD38F2230WWYTQ0@FBGA88 [DX5005]
RD38F2230WWZBQ0@FBGA88 [DX5005]
RD38F2230WWZDQ0@FBGA88 [DX5005]
RD38F2230WWZTQ0@FBGA88 [DX5005]
RD38F2240WWYBQ0@FBGA88 [DX5005]
RD38F2240WWYDQ0@FBGA88 [DX5005]
RD38F2240WWYTQ0@FBGA88 [DX5005]
RD38F2240WWZBQ0@FBGA88 [DX5005]
RD38F2240WWZDQ0@FBGA88 [DX5005]
RD38F2240WWZDQ1@FBGA88 [DX5005]
RD38F2240WWZTQ0@FBGA88 [DX5005]
RD38F3040L0YBQ0@FBGA88 [DX5005]

RD38F3040L0YBQ1@FBGA88 [DX5005]
RD38F3040L0YBQ2@FBGA88 [DX5005]
RD38F3040L0YCQ0@FBGA88 [DX5005]
RD38F3040L0YTQ0@FBGA88 [DX5005]
RD38F3040L0YTQ1@FBGA88 [DX5005]
RD38F3040L0YTQ2@FBGA88 [DX5005]
RD38F3040L0YUQ0@FBGA88 [DX5005]
RD38F3040L0ZBQ0@FBGA88 [DX5005]
RD38F3040L0ZTQ0@FBGA88 [DX5005]
RD38F3050L0YBQ1@FBGA88 [DX5005]
RD38F3050L0YBQ2@FBGA88 [DX5005]
RD38F3050L0YCQ0@FBGA88 [DX5005]
RD38F3050L0YTQ1@FBGA88 [DX5005]
RD38F3050L0YTQ2@FBGA88 [DX5005]
RD38F3050L0YUQ0@FBGA88 [DX5005]
RD38F3050L0ZBQ0@FBGA88 [DX5005]
RD38F3050L0ZBQ1@FBGA88 [DX5005]
RD38F3050L0ZTQ0@FBGA88 [DX5005]
RD38F3050L0ZTQ1@FBGA88 [DX5005]
RD38F3340LLYDQ0@FBGA88 [DX5005]
RD38F3340LLYDQ1@FBGA88 [DX5005]
RD38F3350LLZDQ0@FBGA88 [DX5005]
RD38F3350WWZDQ0@FBGA88 [DX5005]
RD38F3350WWZDQ1@FBGA88 [DX5005]
RD38F4050L0YBQ0@FBGA88 [DX5001]
RD38F4050L0YBQ1@FBGA88 [DX5001]
RD38F4050L0YBQ2@FBGA88 [DX5001]
RD38F4050L0YCQ0@FBGA88 [DX5001]
RD38F4050L0YTQ0@FBGA88 [DX5001]
RD38F4050L0YTQ1@FBGA88 [DX5001]
RD38F4050L0YTQ2@FBGA88 [DX5001]
RD38F4050L0YUQ0@FBGA88 [DX5001]
RD38F4050L0ZBQ0@FBGA88 [DX5001]
RD38F4050L0ZBQ1@FBGA88 [DX5001]
RD38F4050L0ZTQ0@FBGA88 [DX5001]
RD38F4050L0ZTQ1@FBGA88 [DX5001]
RD38F4055L0YBQ2@FBGA88 [DX5001]
RD38F4055L0YTQ2@FBGA88 [DX5001]
RD38F4055L0ZBQ0@FBGA88 [DX5001]
RD38F4055L0ZTQ0@FBGA88 [DX5001]
RD38F4350LLYBQ0@FBGA88 [DX5001]
RD38F4350LLYBQ1@FBGA88 [DX5001]
RD38F4350LLYTQ0@FBGA88 [DX5001]
RD38F4350LLYTQ1@FBGA88 [DX5001]
RD38F4450LLYBQ0@FBGA88 [DX5001]
RD38F4450LLYTQ0@FBGA88 [DX5001]
RD38F4450LVYBQ0@FBGA88 [DX5001]
RD38F4450LVYBQ2@FBGA88 [DX5001]
RD38F4450LVYTQ0@FBGA88 [DX5001]
RD38F4450LVYTQ2@FBGA88 [DX5001]
RD38F4455LLYBQ0@FBGA88 [DX50UN]
RD38F4455LLYBQ1@FBGA88 [DX50UN]
RD38F4455LLYBQ2@FBGA88 [DX50UN]
RD38F4455LLYTQ0@FBGA88 [DX50UN]
RD38F4455LLYTQ1@FBGA88 [DX50UN]
RD38F4455LLYTQ2@FBGA88 [DX50UN]
RD38F4460LVYBB0@FBGA103 [DX5005]
RD38F4460LVYGB0@FBGA103 [DX5056]
RD38F4460LVYTB0@FBGA103 [DX5056]
RD48F2000L0YBQ0@FBGA88 [DX5005]
RD48F2000L0YTQ0@FBGA88 [DX5005]
RD48F2000L0ZBQ0@FBGA88 [DX5005]
RD48F2000L0ZTQ0@FBGA88 [DX5005]
RD48F2000P0XBQ0@FBGA88 [DX5005]
RD48F2000P0XTQ0@FBGA88 [DX5005]
RD48F2000P0ZBQ0@FBGA88 [DX5005]
RD48F2000P0ZTQ0@FBGA88 [DX5005]
RD48F2000W0YBQ0@FBGA88 [DX5005]
RD48F2000W0YTQ0@FBGA88 [DX5005]
RD48F2000W0ZBQ0@FBGA88 [DX5005]
RD48F2000W0ZTQ0@FBGA88 [DX5005]
RD48F2100W0YBQ0@FBGA88 [DX5005]
RD48F2100W0YDQE@FBGA88 [DX5005]
RD48F2100W0YTQ0@FBGA88 [DX5005]
RD48F2200W0YBQ0@FBGA88 [DX5005]
RD48F2200W0YDQ0@FBGA88 [DX5005]
RD48F2200W0YTQ0@FBGA88 [DX5005]
RD48F2200W0ZBQ0@FBGA88 [DX5005]
RD48F2200W0ZDQ0@FBGA88 [DX5005]
RD48F2200W0ZTQ0@FBGA88 [DX5005]
RD48F3000L0YBQ0@FBGA88 [DX5005]
RD48F3000L0YTQ0@FBGA88 [DX5005]
RD48F3000L0ZBQ0@FBGA88 [DX5005]
RD48F3000L0ZTQ0@FBGA88 [DX5005]
RD48F3000P0XBQ0@FBGA88 [DX5005]
RD48F3000P0XTQ0@FBGA88 [DX5005]
RD48F3000P0ZBQ0@FBGA88 [DX5005]
RD48F3000P0ZBQE@FBGA88 [DX5005]
RD48F3000P0ZTQ0@FBGA88 [DX5005]
RD48F3000P0ZTQE@FBGA88 [DX5005]
RD48F3000W0YBQ0@FBGA88 [DX5005]
RD48F3000W0YTQ0@FBGA88 [DX5005]
RD48F3000W0ZBQ0@FBGA88 [DX5005]
RD48F3000W0ZTQ0@FBGA88 [DX5005]
RD48F3300L0YDQ0@FBGA88 [DX5005]
RD48F3300L0ZDQ0@FBGA88 [DX5005]

RD48F3300W0YBQ0@FBGA88 [DX5005]
RD48F3300W0YDQ0@FBGA88 [DX5005]
RD48F3300W0YTQ0@FBGA88 [DX5005]
RD48F4000L0YBQ0@FBGA88 [DX5001]
RD48F4000L0YTQ0@FBGA88 [DX5001]
RD48F4000P0XBQ0@FBGA88 [DX5001]
RD48F4000P0XTQ0@FBGA88 [DX5001]
RD48F4000P0ZBQ0@FBGA88 [DX5001]
RD48F4000P0ZTQ0@FBGA88 [DX5001]
RD48F4040LVYBQ0(BEEP)@FBGA88 [DX5001]
RD48F4040LVYBQ0(BP)@FBGA88 [DX5001]
RD48F4040LVYTQ0(BEEP)@FBGA88 [DX5001]
RD48F4040LVYTQ0(BP)@FBGA88 [DX5001]
RD48F4040LVZBQ0(BEEP)@FBGA88 [DX5001]
RD48F4040LVZBQ0(BP)@FBGA88 [DX5001]
RD48F4040LVZTQ0(BEEP)@FBGA88 [DX5001]
RD48F4040LVZTQ0(BP)@FBGA88 [DX5001]
RD48F4400L0YDQ0@FBGA88 [DX5001]
RD48F4400L0ZDN0@FBGA88 [DX5001]
RD48F4400L0ZDQ0@FBGA88 [DX5001]
RD48F4400P0TBQ0@FBGA88 [DX5001]
RD48F4400P0VBQ0@FBGA88 [DX5001]
RD48F4400P0VTQ0@FBGA88 [DX5001]
RD48F4440LVYBQ0@FBGA88 [DX5001]
RD48F4444LLZBB0@FBGA103 [DX5005]
RD48F4444LVYBB0@FBGA103 [DX50UN]
RF48F4400P0VBQE@FBGA88 [DX5001]
TB28F004S3@PSOP44 [DX1014]
TB28F004S5@PSOP44 [DX1014]
TB28F004SC@PSOP44 [DX1014]
TB28F008S3@PSOP44 [DX1014]
TB28F008S5@PSOP44 [DX1014]
TB28F008SA@PSOP44 [DX1014]
TB28F008SA-L@PSOP44 [DX1014]
TB28F008SC@PSOP44 [DX1014]
TB28F016S3@PSOP44 [DX1014]
TB28F016S5@PSOP44 [DX1014]
TB28F016SC@PSOP44 [DX1014]
TB28F200B5B@PSOP44 [DX1014]
TB28F200B5T@PSOP44 [DX1014]
TB28F200BVB@PSOP44 [DX1014]
TB28F200BVT@PSOP44 [DX1014]
TB28F200BXB@PSOP44 [DX1014]
TB28F200BXT@PSOP44 [DX1014]
TB28F400B5B@PSOP44 [DX1014]
TB28F400B5T@PSOP44 [DX1014]
TB28F400BVB@PSOP44 [DX1014]
TB28F400BVT@PSOP44 [DX1014]
TB28F400BXB@PSOP44 [DX1014]
TB28F400BXT@PSOP44 [DX1014]
TB28F800B5B@PSOP44 [DX1014]
TB28F800B5T@PSOP44 [DX1014]
TB28F800BVB@PSOP44 [DX1014]
TB28F800BVT@PSOP44 [DX1014]
TE28F002BEB@TSOP40 [DX1006]
TE28F002BET@TSOP40 [DX1006]
TE28F002BVB@TSOP40 [DX1006]
TE28F002BVT@TSOP40 [DX1006]
TE28F002BXB@TSOP40 [DX1006]
TE28F002BXT@TSOP40 [DX1006]
TE28F004BEB@TSOP40 [DX1006]
TE28F004BET@TSOP40 [DX1006]
TE28F004BVB@TSOP40 [DX1006]
TE28F004BVT@TSOP40 [DX1006]
TE28F004BXB@TSOP40 [DX1006]
TE28F004BXT@TSOP40 [DX1006]
TE28F004S3@TSOP40 [DX1006]
TE28F004S5@TSOP40 [DX1006]
TE28F004SC@TSOP40 [DX1006]
TE28F008B3B@TSOP40 [DX1006]
TE28F008B3BA@TSOP40 [DX1006]
TE28F008B3T@TSOP40 [DX1006]
TE28F008B3TA@TSOP40 [DX1006]
TE28F008BEB@TSOP40 [DX1006]
TE28F008BET@TSOP40 [DX1006]
TE28F008BVB@TSOP40 [DX1006]
TE28F008BVT@TSOP40 [DX1006]
TE28F008C3BA@TSOP40 [DX1006]
TE28F008C3TA@TSOP40 [DX1006]
TE28F008S3@TSOP40 [DX1006]
TE28F008S5@TSOP40 [DX1006]
TE28F008SA@TSOP40 [DX1006]
TE28F008SA-L@TSOP40 [DX1006]
TE28F008SC@TSOP40 [DX1006]
TE28F016B3B@TSOP40 [DX1006]
TE28F016B3T@TSOP40 [DX1006]
TE28F016C3BA@TSOP40 [DX1006]

TE28F016C3TA@TSOP40 [DX1006]
TE28F016S3@TSOP40 [DX1006]
TE28F016S5@TSOP40 [DX1006]
TE28F016SC@TSOP40 [DX1006]
TE28F128J3C@TSOP56 [DX1011]
TE28F128J3D@TSOP56 [DX1011]
TE28F128J3F@TSOP56 [DX1011]
TE28F128P30B@TSOP56 [DX1011]
TE28F128P30BF@TSOP56 [DX1011]
TE28F128P30T@TSOP56 [DX1011]
TE28F128P30TF@TSOP56 [DX1011]
TE28F128P33B@TSOP56 [DX1011]
TE28F128P33BF@TSOP56 [DX1011]
TE28F128P33T@TSOP56 [DX1011]
TE28F128P33TF@TSOP56 [DX1011]
TE28F160B3B@TSOP48 [DX1004]
TE28F160B3BA@TSOP48 [DX1004]
TE28F160B3BC@TSOP48 [DX1004]
TE28F160B3BD@TSOP48 [DX1004]
TE28F160B3T@TSOP48 [DX1004]
TE28F160B3TA@TSOP48 [DX1004]
TE28F160B3TC@TSOP48 [DX1004]
TE28F160B3TD@TSOP48 [DX1004]
TE28F160C3BA@TSOP48 [DX1004]
TE28F160C3BC@TSOP48 [DX1004]
TE28F160C3BD@TSOP48 [DX1004]
TE28F160C3TA@TSOP48 [DX1004]
TE28F160C3TC@TSOP48 [DX1004]
TE28F160C3TD@TSOP48 [DX1004]
TE28F160F3B@TSOP56 [DX1055]
TE28F160F3T@TSOP56 [DX1055]
TE28F160S3@TSOP56 [DX1055]
TE28F160S5@TSOP56 [DX1055]
TE28F200B5B@TSOP48 [DX1004]
TE28F200B5T@TSOP48 [DX1004]
TE28F200BVB@TSOP56 [DX1055]
TE28F200BVT@TSOP56 [DX1055]
TE28F200BXB@TSOP56 [DX1055]
TE28F200BXT@TSOP56 [DX1055]
TE28F200CEB@TSOP56 [DX1055]
TE28F200CET@TSOP56 [DX1055]
TE28F200CVB@TSOP48 [DX1004]
TE28F200CVT@TSOP48 [DX1004]
TE28F256J3C@TSOP56 [DX1011]
TE28F256J3D@TSOP56 [DX1011]
TE28F256J3F@TSOP56 [DX1011]
TE28F256P30B@TSOP56 [DX1011]
TE28F256P30BF@TSOP56 [DX1011]
TE28F256P30T@TSOP56 [DX1011]
TE28F256P30TF@TSOP56 [DX1011]
TE28F256P33B@TSOP56 [DX1011]
TE28F256P33BF@TSOP56 [DX1011]
TE28F256P33T@TSOP56 [DX1011]
TE28F256P33TF@TSOP56 [DX1011]
TE28F320B3B@TSOP48 [DX1004]
TE28F320B3BA@TSOP48 [DX1004]
TE28F320B3BC@TSOP48 [DX1004]
TE28F320B3BD@TSOP48 [DX1004]
TE28F320B3T@TSOP48 [DX1004]
TE28F320B3TA@TSOP48 [DX1004]
TE28F320B3TC@TSOP48 [DX1004]
TE28F320B3TD@TSOP48 [DX1004]
TE28F320C3BA@TSOP48 [DX1004]
TE28F320C3BC@TSOP48 [DX1004]
TE28F320C3BD@TSOP48 [DX1004]
TE28F320C3TA@TSOP48 [DX1004]
TE28F320C3TC@TSOP48 [DX1004]
TE28F320C3TD@TSOP48 [DX1004]
TE28F320J3C@TSOP56 [DX1011]
TE28F320J3D@TSOP56 [DX1011]
TE28F320J3F@TSOP56 [DX1011]
TE28F400B3B@TSOP48 [DX1004]
TE28F400B3T@TSOP48 [DX1004]
TE28F400B5B@TSOP48 [DX1004]
TE28F400B5T@TSOP48 [DX1004]
TE28F400BVB@TSOP56 [DX1055]
TE28F400BVT@TSOP56 [DX1055]
TE28F400BXB@TSOP56 [DX1055]
TE28F400BXT@TSOP56 [DX1055]
TE28F400CEB@TSOP48 [DX1004]
TE28F400CET@TSOP48 [DX1004]
TE28F400CVB@TSOP48 [DX1004]
TE28F400CVT@TSOP48 [DX1004]
TE28F640B3BC@TSOP48 [DX1004]
TE28F640B3TC@TSOP48 [DX1004]
TE28F640C3BC@TSOP48 [DX1004]
TE28F640C3TC@TSOP48 [DX1004]
TE28F640J3C@TSOP56 [DX1011]
TE28F640J3D@TSOP56 [DX1011]
TE28F640J3F@TSOP56 [DX1011]
TE28F640P30B@TSOP56 [DX1011]
TE28F640P30T@TSOP56 [DX1011]
TE28F640P33B@TSOP56 [DX1011]
TE28F640P33T@TSOP56 [DX1011]
TE28F800B3B@TSOP48 [DX1004]
TE28F800B3BA@TSOP48 [DX1004]

TE28F800B3T@TSOP48 [DX1004]
TE28F800B3TA@TSOP48 [DX1004]
TE28F800B5B@TSOP48 [DX1004]
TE28F800B5T@TSOP48 [DX1004]
TE28F800C3BA@TSOP48 [DX1004]
TE28F800C3BD@TSOP48 [DX1004]
TE28F800C3TA@TSOP48 [DX1004]
TE28F800C3TD@TSOP48 [DX1004]
TE28F800CEB@TSOP48 [DX1004]
TE28F800CET@TSOP48 [DX1004]
TE28F800CVB@TSOP48 [DX1004]
TE28F800CVT@TSOP48 [DX1004]
TE28F800F3B@TSOP56 [DX1055]
TE28F800F3T@TSOP56 [DX1055]
TE48F4400P0TB00@TSOP56 [DX1011]
TE48F4400P0VB00@TSOP56 [DX1011]
TE48F4400P0VT00@TSOP56 [DX1011]

PLD

5C031 [DX0001]
5C031@PLCC20 [DX2020]
5C032 [DX0001]
5C032@PLCC20 [DX2020]
5C060 [DX0001]
5C060@PLCC28 [DX2028]
5C090 [DX0001]
5C090@PLCC44 [DX2044]
5C180@PLCC68 [DX2068]
85C060 [DX0001]
85C060@PLCC28 [DX2028]
85C090 [DX0001]
85C090@PLCC44 [DX2044]
85C220 [DX0001]
85C220@PLCC20 [DX2020]
IPLD910 [DX0001]
IPLD910@PLCC44 [DX2044]

MICROCONTROLLER

8741 [DX0001]
8741A [DX0001]
8742 [DX0001]
8744 [DX0001]
8744H [DX0001]
8748 [DX0001]
8748(25V) [DX0001]
8748H [DX0001]
8749 [DX0001]
8749H [DX0001]
8751 [DX0001]
8751BH [DX0001]
8751BH@PLCC44 [DX2044]
8751H [DX0001]
8751H-8 [DX0001]
8752BH [DX0001]
8752BH@PLCC44 [DX2044]
8796BH@PLCC68 [DX2068]
8796JF@PLCC68 [DX2068]
8797BH@PGA68 [DX5000]
8797BH@PLCC68 [DX2068]
8797JF@PGA68 [DX5000]
8797JF@PLCC68 [DX2068]
8798 [DX0001]
87C151SA [DX0001]
87C151SA@PLCC44 [DX2044]
87C151SB [DX0001]
87C151SB@PLCC44 [DX2044]
87C194@PLCC52 [DX2052]
87C196CA@PGA68 [DX5000]
87C196CA@PLCC68 [DX2068]
87C196CB@PLCC84 [DX2084]
87C196CB@PQFP100 [DX3022]
87C196JQ@PLCC52 [DX2052]
87C196JR@PLCC52 [DX2052]
87C196JT@PLCC52 [DX2052]
87C196JV@PLCC52 [DX2052]
87C196KB@PGA68 [DX5000]
87C196KB@PLCC68 [DX2068]
87C196KC@PGA68 [DX5000]
87C196KC@PLCC68 [DX2068]
87C196KD@PGA68 [DX5000]
87C196KD@PLCC68 [DX2068]
87C196KQ@PGA68 [DX5000]

87C196KQ@PLCC68 [DX2068]
87C196KR@PLCC68 [DX2068]
87C196KS@PLCC68 [DX2068]
87C196KT@PLCC68 [DX2068]
87C196LB@PLCC52 [DX2052]
87C196MC@PQFP80 [DX3019]
87C196MH@PLCC84 [DX2084]
87C196MH@SDIP64 [DX0064]
87C251SA [DX0001]
87C251SB [DX0001]
87C251SP [DX0001]
87C251SQ [DX0001]
87C51 [DX0001]
87C51@TQFP44 [DX3002]
87C51FA@PLCC44 [DX2044]
87C51FB [DX0001]
87C51FB@TQFP44 [DX3002]
87C51FC@PLCC44 [DX2044]
87C51GB@PLCC68 [DX2068]
87C51RA@PLCC44 [DX2044]
87C51RB [DX0001]
87C51RB@TQFP44 [DX3002]
87C51RC@PLCC44 [DX2044]
87C52 [DX0001]
87C52@TQFP44 [DX3002]
87C54@PLCC44 [DX2044]
87C58 [DX0001]
87C58@TQFP44 [DX3003]
87L51FA@PLCC44 [DX2044]
87L51FB [DX0001]
87L51FB@TQFP44 [DX3002]
87L51FC@TQFP44 [DX3003]
87L52@PLCC44 [DX2044]
87L54@PLCC44 [DX2044]
87L58@PLCC44 [DX2044]
AS87C196CB@PLCC84 [DX2084]
D8741A [DX0001]
D8748H [DX0001]
D8749H [DX0001]
D8751H [DX0001]
MD8748 [DX0001]
MD8749 [DX0001]
P8748 [DX0001]
P8749 [DX0001]
87C196KR@PGA68 [DX5000]
87C196KS@PGA68 [DX5000]
87C196KT@PGA68 [DX5000]
87C196LA@PLCC52 [DX2052]
87C196MC@PLCC84 [DX2084]
87C196MC@SDIP64 [DX0064]
87C196MH@PQFP80 [DX3019]
87C198@PLCC52 [DX2052]
87C251SA@PLCC44 [DX2044]
87C251SB@PLCC44 [DX2044]
87C251SP@PLCC44 [DX2044]
87C251SQ@PLCC44 [DX2044]
87C51@PLCC44 [DX2044]
87C51FA [DX0001]
87C51FA@TQFP44 [DX3002]
87C51FB@PLCC44 [DX2044]
87C51FC [DX0001]
87C51FC@TQFP44 [DX3003]
87C51RA [DX0001]
87C51RA@TQFP44 [DX3002]
87C51RB@PLCC44 [DX2044]
87C51RC [DX0001]
87C51RC@TQFP44 [DX3003]
87C52@PLCC44 [DX2044]
87C54 [DX0001]
87C54@TQFP44 [DX3003]
87C58@PLCC44 [DX2044]
87L51FA [DX0001]
87L51FA@TQFP44 [DX3002]
87L51FB@PLCC44 [DX2044]
87L51FC@PLCC44 [DX2044]
87L52 [DX0001]
87L52@TQFP44 [DX3002]
87L54@TQFP44 [DX3003]
87L58@TQFP44 [DX3003]
AS87C196CB@PQFP100 [DX3022]
D8748 [DX0001]
D8749 [DX0001]
D8751 [DX0001]
D8751H-8 [DX0001]
MD8748H [DX0001]
MD8749H [DX0001]
P8748H [DX0001]
P8749H [DX0001]

INTELSIL

E(E)PROM/FRAM/NVRAM

HS-6617RH [DX0001]
HS-6617RH-T [DX0001]
HS-6664RH [DX0001]
HS-6664RH-T [DX0001]
HS-6883RH [DX0001]
HS-6883RH-T [DX0001]
HS-6617RH@SOIC24 [DX1033]
HS-6617RH-T@SOIC24 [DX1033]
HS-6664RH@SOIC28 [DX1033]
HS-6664RH-T@SOIC28 [DX1033]
HS-6883RH@SOIC24 [DX1033]
HS-6883RH-T@SOIC24 [DX1033]

INTERSIL

E(E)PROM/FRAM/NVRAM

X4043 [DX0001]
X4043@SOIC8 [DX1045]
X4045@MSOP8 [DX1000]
X4043@MSOP8 [DX1000]
X4045 [DX0001]
X4045@SOIC8 [DX1045]

Intretech

MICROCONTROLLER

C8051T321-GR [DX4013]

IR

MICROCONTROLLER

IRMCF171@QFP48(LeftDown) [DX3091-A]
IRMCF188@QFP64 [DX3133]
IRMCK171@QFP48(LeftDown) [DX3091-A]
IRMCK311@QFP64(LeftUp) [DX3105]
IRMCK341@QFP64(LeftUp) [DX3096]
IRMCK343@QFP64(LeftUp) [DX3096]
IRMCK171@QFP48 [DX3091]
IRMCK341@QFP64 [DX3096-A]
IRMCK343@QFP64 [DX3096-A]

ISGAL

MICROCONTROLLER

ISGAL1 [DX0001]
ISGAL2 [DX0001]

ISSI

E(E)PROM/FRAM/NVRAM

IS24C01 [DX0001]
IS24C01@SOIC8 [DX1045]
IS24C01B [DX0001]
IS24C01B@SOIC8 [DX1045]
IS24C01C [DX0001]
IS24C01C@SOIC8 [DX1045]
IS24C02 [DX0001]
IS24C02@SOIC8 [DX1045]
IS24C02A [DX0001]
IS24C02A@MSOP8 [DX1015]
IS24C02A@TSSOP8 [DX1059]
IS24C02B@DFN8
IS24C02B@SOIC8 [DX1045]
IS24C02C [DX0001]
IS24C02C@MSOP8 [DX1015]
IS24C02C@TSSOP8 [DX1059]
IS24C02E@DFN8
IS24C02E@SOIC8 [DX1045]
IS24C04 [DX0001]
IS24C04@SOIC8 [DX1045]
IS24C04A [DX0001]
IS24C04A@MSOP8 [DX1015]
IS24C04A@TSSOP8 [DX1059]
IS24C04B@DFN8
IS24C04B@SOIC8 [DX1045]
IS24C08 [DX0001]
IS24C08@SOIC8 [DX1045]
IS24C08A [DX0001]
IS24C08A@MSOP8 [DX1015]
IS24C08A@TSSOP8 [DX1059]
IS24C08B@DFN8
IS24C08B@SOIC8 [DX1045]
IS24C128 [DX0001]
IS24C128@TSSOP14 [DX1000]
IS24C128B@SOIC8 [DX1045]
IS24C16 [DX0001]
IS24C16@SOIC8 [DX1045]
IS24C16A [DX0001]
IS24C16A@SOIC8 [DX1045]
IS24C16B [DX0001]
IS24C16B@SOIC8 [DX1045]
IS24C256 [DX0001]
IS24C256@TSSOP14 [DX1000]
IS24C256A@SOIC8 [DX1045]
IS24C256C [DX0001]
IS24C256C@TSSOP14 [DX1000]
IS24C32@SOIC8 [DX1045]
IS24C32A [DX0001]
IS24C01@MSOP8 [DX1015]
IS24C01@TSSOP8 [DX1059]
IS24C01B@MSOP8 [DX1015]
IS24C01B@TSSOP8 [DX1059]
IS24C01C@MSOP8 [DX1015]
IS24C01C@TSSOP8 [DX1059]
IS24C02@MSOP8 [DX1015]
IS24C02@TSSOP8 [DX1059]
IS24C02A@DFN8
IS24C02A@SOIC8 [DX1045]
IS24C02B [DX0001]
IS24C02B@MSOP8 [DX1015]
IS24C02B@TSSOP8 [DX1059]
IS24C02C@DFN8
IS24C02C@SOIC8 [DX1045]
IS24C02E [DX0001]
IS24C02E@MSOP8 [DX1015]
IS24C02E@TSSOP8 [DX1059]
IS24C04@MSOP8 [DX1015]
IS24C04@TSSOP8 [DX1059]
IS24C04A@DFN8
IS24C04A@SOIC8 [DX1045]
IS24C04B [DX0001]
IS24C04B@MSOP8 [DX1015]
IS24C04B@TSSOP8 [DX1059]
IS24C08@MSOP8 [DX1015]
IS24C08@TSSOP8 [DX1059]
IS24C08A@DFN8
IS24C08A@SOIC8 [DX1045]
IS24C08B [DX0001]
IS24C08B@MSOP8 [DX1015]
IS24C08B@TSSOP8 [DX1059]
IS24C128@SOIC8 [DX1045]
IS24C128B [DX0001]
IS24C128B@TSSOP14 [DX1000]
IS24C16@MSOP8 [DX1015]
IS24C16@TSSOP8 [DX1059]
IS24C16A@MSOP8 [DX1015]
IS24C16A@TSSOP8 [DX1059]
IS24C16B@MSOP8 [DX1015]
IS24C16B@TSSOP8 [DX1059]
IS24C256@SOIC8 [DX1045]
IS24C256A [DX0001]
IS24C256A@TSSOP14 [DX1000]
IS24C256C@SOIC8 [DX1045]
IS24C32 [DX0001]
IS24C32@TSSOP8 [DX1059]
IS24C32A@MSOP8 [DX1015]

IS24C32A@SOIC8 [DX1045]
IS24C32A@TSSOP8 [DX1059]
IS24C32B [DX0001]
IS24C32B@SOIC8 [DX1045]
IS24C32B@TSSOP8 [DX1059]
IS24C32C [DX0001]
IS24C32C@DFN8 [DX4047]
IS24C32C@MSOP8 [DX1015]
IS24C32C@SOIC8 [DX1045]
IS24C32C@TSSOP8 [DX1059]
IS24C64 [DX0001]
IS24C64@SOIC8 [DX1045]
IS24C64@TSSOP8 [DX1059]
IS24C64A [DX0001]
IS24C64A@MSOP8 [DX1015]
IS24C64A@SOIC8 [DX1045]
IS24C64A@TSSOP8 [DX1059]
IS24C64B [DX0001]
IS24C64B@SOIC8 [DX1045]
IS24C64B@TSSOP8 [DX1059]
IS24C64C [DX0001]
IS24C64C@MSOP8 [DX1015]
IS24C64C@SOIC8 [DX1045]
IS24C64C@TSSOP8 [DX1059]
IS24L128 [DX0001]
IS24L128@SOIC8(150mil) [DX1045]
IS24L128@SOIC8(200mil) [DX1044]
IS24L256 [DX0001]
IS24L256@SOIC8(150mil) [DX1045]
IS24L256@SOIC8(200mil) [DX1044]
IS25C01 [DX0001]
IS25C01@SOIC8 [DX1045]
IS25C01@TSSOP8 [DX1059]
IS25C02 [DX0001]
IS25C02@SOIC8 [DX1045]
IS25C02@TSSOP8 [DX1059]
IS25C04 [DX0001]
IS25C04@SOIC8 [DX1045]
IS25C04@TSSOP8
IS25C08 [DX0001]
IS25C08@SOIC8 [DX1045]
IS25C08@TSSOP8 [DX1059]
IS25C128@SOIC8 [DX1045]
IS25C128@TSSOP8 [DX1059]
IS25C128A-S8 [DX1045]
IS25C128A-T8 [DX1059]
IS25C16 [DX0001]
IS25C16@SOIC8 [DX1045]
IS25C16@TSSOP8 [DX1059]
IS25C256@SOIC8 [DX1045]
IS25C256@TSSOP8 [DX1059]
IS25C256A@SOIC8 [DX1045]
IS25C256A@TSSOP8 [DX1059]
IS25C32A [DX0001]
IS25C32A@SOIC8 [DX1045]
IS25C32A@TSSOP8 [DX1059]
IS25C32B [DX0001]
IS25C32B@SOIC8 [DX1045]
IS25C32B@TSSOP8 [DX1059]
IS25C64A [DX0001]
IS25C64A@SOIC8 [DX1045]
IS25C64A@TSSOP8 [DX1059]
IS25C64B [DX0001]
IS25C64B@SOIC8 [DX1045]
IS25C64B@TSSOP8 [DX1059]
IS25CD010@SOIC8[150 mil] [DX1045#1]
IS25CD010@SOIC8[200 mil] [DX1059#3]
IS25CD010@WSON8 [DX4005#1]
IS25CD025@SOIC8 [DX1045#1]
IS25CD025@TSSOP8 [DX1059#3]
IS25CD512 [DX0001]
IS25CD512@SOIC8[150mil] [DX1045#1]
IS25CD512@SOIC8[200mil] [DX1044#1]
IS25CD512@TSSOP8 [DX1000#1]
IS25CD512@USON8 [DX4002#1]
IS25CD512@WSON8 [DX4005#1]
IS25CQ032C@SOIC8 [DX1044#1]
IS25CQ032C@WSON8 [DX4006#1]
IS25LD010@SOIC8 [DX1045#1]
IS25LD010@TSSOP8 [DX1059#3]
IS25LD010@WSON8 [DX4005#1]
IS25LD020@SOIC8 [DX1045#1]
IS25LD020@TSSOP8 [DX1059#3]
IS25LD020@WSON8 [DX4005#1]
IS25LD040@SOIC8 [DX1045#1]
IS25LD040@WSON8 [DX4005#1]
IS25LD040-B8 [DX1044#1]
IS25LD256C@SOIC8 [DX1045#1]
IS25LD256C@TSSOP8 [DX1059#3]
IS25LD256C@WSON8 [DX4005#1]
IS25LD512@SOIC8 [DX1045#1]

IS25LD512@TSSOP8 [DX1059#3]
IS25LD512@WSON8 [DX4005#1]
IS25LP032@SOIC16 [DX1072#1]
IS25LP032@SOIC8 [DX1044#1]
IS25LP032@TFBGA24 [DX5146]
IS25LP032@USON8 [DX4005#1]
IS25LP032@VSOP8 [DX1044#1]
IS25LP032@WSON8 [DX4006#1]
IS25LP064@SOIC16 [DX1072#1]
IS25LP064@SOIC8 [DX1044#1]
IS25LP064@TFBGA24 [DX5146]
IS25LP064@USON8 [DX4005#1]
IS25LP064@VSOP8 [DX1044#1]
IS25LP064@WSON8 [DX4006#1]
IS25LP128@SOIC16 [DX1072#1]
IS25LP128@SOIC8 [DX1044#1]
IS25LP128@TFBGA24 [DX5146]
IS25LP128@USON8 [DX4005#1]
IS25LP128@VSOP8 [DX1044#1]
IS25LP128@WSON8 [DX4006#1]
IS25LQ010A@SOIC8[150 mil] [DX1045#1]
IS25LQ010A@SOIC8[200 mil] [DX1059#3]
IS25LQ010A@WSON8 [DX4005#1]
IS25LQ016@SOP8 [DX1048-1]
IS25LQ016@TSOP8 [DX1044#1]
IS25LQ016@USON8 [DX4005#1]
IS25LQ016@WSON8 [DX4005#1]
IS25LQ016B@SOP8[150 mil] [DX1045#1]
IS25LQ016B@SOP8[200 mil] [DX1048-1]
IS25LQ016B@TSOP8 [DX1044#1]
IS25LQ016B@USON8 [DX4005#1]
IS25LQ016B@WSON8 [DX4005#1]
IS25LQ020A@SOIC8[150 mil] [DX1045#1]
IS25LQ020A@SOIC8[200 mil] [DX1059#3]
IS25LQ020A@WSON8 [DX4005#1]
IS25LQ025B@SOIC8[150 mil] [DX1045#1]
IS25LQ025B@SOIC8[200 mil] [DX1044#1]
IS25LQ025B@TSSOP8 [DX1059#3]
IS25LQ025B@USON8 [DX4002#1]
IS25LQ025B@VSOP8 [DX1045#1]
IS25LQ025B@WSON8 [DX4005#1]
IS25LQ032B@SOIC16 [DX1072#1]
IS25LQ032B@SOIC8 [DX1044#1]
IS25LQ032B@WSON8 [DX4006#1]
IS25LQ032C@SOIC8 [DX1044#1]
IS25LQ032C@WSON8 [DX4006#1]
IS25LQ080@SOIC8[150 mil] [DX1045#1]
IS25LQ080@SOIC8[200 mil] [DX1044#1]
IS25LQ080@VVSOP8 [DX1045#1]
IS25LQ080@WSON8 [DX4005#1]
IS25LQ080B@SOIC8[150 mil] [DX1045#1]
IS25LQ080B@SOIC8[200 mil] [DX1044#1]
IS25LQ080B@VVSOP8 [DX1045#1]
IS25LQ080B@WSON8 [DX4005#1]
IS25LQ512B@SOIC8[150 mil] [DX1045#1]
IS25LQ512B@SOIC8[200 mil] [DX1044#1]
IS25LQ512B@TSSOP8 [DX1059#3]
IS25LQ512B@USON8 [DX4002#1]
IS25LQ512B@VSOP8 [DX1045#1]
IS25LQ512B@WSON8 [DX4005#1]
IS25WD020@SOIC8(150mil) [DX1045#1]
IS25WD020@SOIC8(200mil) [DX1044#1]
IS25WD020@VVSOP8 [DX1045#1]
IS25WD020@WSON8 [DX4005#1]
IS25WD040@SOIC8(150mil) [DX1045#1]
IS25WD040@SOIC8(200mil) [DX1044#1]
IS25WD040@VVSOP8 [DX1045#1]
IS25WD040@WSON8 [DX4005#1]
IS27C010 [DX0001]
IS27C010@PLCC32 [DX2032]
IS27C010@TSOP32 [DX1002]
IS27C020 [DX0001]
IS27C020@PLCC32 [DX2032]
IS27C020@TSOP32 [DX1002]

IS27C256 [DX0001]
IS27C256@PLCC32 [DX2032]
IS27C512 [DX0001]
IS27C512@PLCC32 [DX2032]
IS27C512@TSOP28 [DX1024]
IS27HC010 [DX0001]
IS27HC010@PLCC32 [DX2032]
IS27HC010@TSOP32 [DX1002]
IS27HC020 [DX0001]
IS27HC020@PLCC32 [DX2032]
IS27HC020@TSOP32 [DX1002]
IS27HC256 [DX0001]
IS27HC256@PLCC32 [DX2032]
IS27HC512 [DX0001]
IS27HC512@PLCC32 [DX2032]
IS27HC512@TSOP28 [DX1024]
IS27LV010 [DX0001]
IS27LV010@PLCC32 [DX2032]
IS27LV010@TSOP32 [DX1002]
IS27LV512 [DX0001]
IS27LV512@PLCC32 [DX2032]
IS27LV512@TSOP28 [DX1024]
IS28F010 [DX0001]
IS28F010@PLCC32 [DX2032]
IS28F010@TSOP32 [DX1002]
IS28F010A [DX0001]
IS28F010A@PLCC32 [DX2032]
IS28F010A@TSOP32 [DX1002]
IS28F020 [DX0001]
IS28F020@PLCC32 [DX2032]
IS28F020@TSOP32 [DX1002]
IS29F010 [DX0001]
IS29F010@PLCC32 [DX2032]
IS29F010@TSOP32 [DX1002]
IS29GL064B@FBGA48 [DX5083]
IS29GL064B@TSOP48 [DX1004]
IS29GL064H@FBGA64 [DX5074]
IS29GL064H@TSOP56 [DX1011]
IS29GL064L@FBGA64 [DX5074]
IS29GL064L@TSOP56 [DX1011]
IS29GL064T@FBGA48 [DX5083]
IS29GL064T@TSOP48 [DX1004]
IS34C02 [DX0001]
IS34C02@MSOP8 [DX1015]
IS34C02@SOIC8 [DX1045]
IS34C02@TSSOP8 [DX1059]
IS34C02B@DFN8
IS34C02B@TSSOP8 [DX1059]
IS71V08F32AS08@FBGA73 [DX5001]
IS71V08F32BS08@FBGA73 [DX5001]
IS71V08F32CS08@FBGA73 [DX5001]
IS71V08F32DS08@FBGA73 [DX5001]
IS71V08F32ES08@FBGA73 [DX5001]
IS71V08F32ESB08@FBGA73 [DX5001]
IS71V08F32EST08@FBGA73 [DX5001]
IS71V08F32FS08@FBGA73 [DX5001]
IS71V08F32GSB08@FBGA73 [DX5001]
IS71V08F32GST08@FBGA73 [DX5001]
IS71V08F64GS08@FBGA101 [DX50UN]
IS71V08F64GS08@FBGA73 [DX5001]
IS71V16F32AS08@FBGA73 [DX5001]
IS71V16F32B04@FBGA56 [DX5045]
IS71V16F32B04@FBGA59 [DX50UN]
IS71V16F32BS08@FBGA73 [DX5001]
IS71V16F32CS08@FBGA73 [DX5001]
IS71V16F32DS08@FBGA73 [DX5001]
IS71V16F32ES08@FBGA73 [DX5001]
IS71V16F32ESB08@FBGA73 [DX5001]
IS71V16F32EST08@FBGA73 [DX5001]
IS71V16F32FS08@FBGA73 [DX5001]
IS71V16F32GSB08@FBGA73 [DX5001]
IS71V16F32GST08@FBGA73 [DX5001]
IS71V16F32T04@FBGA56 [DX5045]
IS71V16F32T04@FBGA59 [DX50UN]
IS71V16F64GS08@FBGA101 [DX50UN]
IS71V16F64GS08@FBGA73 [DX5001]
IS71VPCF32AS04@FBGA73 [DX5001]
IS71VPCF32BS04@FBGA73 [DX5001]
IS71VPCF32CS04@FBGA73 [DX5001]
IS71VPCF32DS04@FBGA73 [DX5001]
IS71VPCF32ES04@FBGA73 [DX5001]
IS71VPCF32FS04@FBGA73 [DX5001]
IS71VPCF64GS08@FBGA65 [DX5048]
IS75V16F64GS16@FBGA65 [DX5048]
IS75V16F64GS32@FBGA65 [DX5048]
IS93C46 [DX0001]
IS93C46@SOIC8 [DX1045]
IS93C46A(08bit) [DX0001]
IS93C46A(08bit)@SOIC8 [DX1045]
IS93C46A(08bit)@TSSOP8 [DX1059]
IS93C46A(16bit) [DX0001]
IS93C46A(16bit)@SOIC8 [DX1045]
IS93C46A(16bit)@TSSOP8 [DX1059]
IS93C46B [DX0001]
IS93C46B@SOIC8 [DX1045]
IS93C46B@TSSOP8 [DX1059]

IS93C46D(08bit) [DX0001]
IS93C46D(08bit)@SOIC8 [DX1045]
IS93C46D(08bit)@TSSOP8 [DX1059]
IS93C46D(16bit) [DX0001]
IS93C46D(16bit)@SOIC8 [DX1045]
IS93C46D(16bit)@TSSOP8 [DX1059]
IS93C56 [DX0001]
IS93C56@SOIC8 [DX1045]
IS93C56A(08bit) [DX0001]
IS93C56A(08bit)@SOIC8 [DX1045]
IS93C56A(08bit)@TSSOP8 [DX1059]
IS93C56A(16bit) [DX0001]
IS93C56A(16bit)@SOIC8 [DX1045]
IS93C56A(16bit)@TSSOP8 [DX1059]
IS93C66 [DX0001]
IS93C66@SOIC8 [DX1045]
IS93C66A(08bit) [DX0001]
IS93C66A(08bit)@SOIC8 [DX1045]
IS93C66A(08bit)@TSSOP8 [DX1059]
IS93C66A(16bit) [DX0001]
IS93C66A(16bit)@SOIC8 [DX1045]
IS93C66A(16bit)@TSSOP8 [DX1059]
IS93C76A(08bit) [DX0001]
IS93C76A(08bit)@SOIC8 [DX1045]
IS93C76A(08bit)@TSSOP8 [DX1059]
IS93C76A(16bit) [DX0001]
IS93C76A(16bit)@SOIC8 [DX1045]
IS93C76A(16bit)@TSSOP8 [DX1059]
IS93C86A(08bit) [DX0001]
IS93C86A(08bit)@SOIC8 [DX1045]
IS93C86A(08bit)@TSSOP8 [DX1059]
IS93C86A(16bit) [DX0001]
IS93C86A(16bit)@SOIC8 [DX1045]
IS93C86A(16bit)@TSSOP8 [DX1059]

DRAM & SRAM

IS61C1024 [DX0001]
IS61C1024(300m)@SOJ32 [DX1038]
IS61C1024(400m)@SOJ32 [DX1039]
IS61C1024@TSOP32 [DX1002]
IS61C1024L [DX0001]
IS61C1024L(300m)@SOJ32 [DX1038]
IS61C1024L(400m)@SOJ32 [DX1039]
IS61C1024L@TSOP32 [DX1002]
IS61C256AH [DX0001]
IS61C256AH@SOJ28
IS61C256AH@TSOP28 [DX1001]
IS61C512 [DX0001]
IS61C512(300m)@SOJ32 [DX1038]
IS61C512(400m)@SOJ32 [DX1039]
IS61C512@TSOP32 [DX1002]
IS61C64AH [DX0001]
IS61C64AH@SOJ28
IS61C64AH@TSOP28 [DX1001]
IS61LV256 [DX0001]
IS61LV256@SOJ28
IS61LV256@TSOP28 [DX1001]
IS61M256 [DX0001]
IS61M256@SOJ28
IS61M256@TSOP28 [DX1001]
IS62C1024 [DX0001]
IS62C1024(300m)@SOJ32 [DX1038]
IS62C1024(400m)@SOJ32 [DX1039]
IS62C1024@TSOP32 [DX1002]
IS62C256 [DX0001]
IS62C256@SOJ28
IS62C256@TSOP28 [DX1001]
IS62C512 [DX0001]
IS62C512(300m)@SOJ32 [DX1038]
IS62C512(400m)@SOJ32 [DX1039]
IS62C512@TSOP32 [DX1002]
IS62C64 [DX0001]
IS62C64@SOJ28
IS62C64@TSOP28 [DX1001]
IS62LV256 [DX0001]
IS62LV256@SOJ28
IS62LV256@TSOP28 [DX1001]

MICROCONTROLLER

IS89C51A [DX0001]
IS89C51A@PLCC44 [DX2044]
IS89C51A@TQFP44 [DX3002]
IS89C52A [DX0001]

IS89C52A@PLCC44 [DX2044] IS89C52A@TQFP44 [DX3002]

JSC

E(E)PROM/FRAM/NVRAM

JS25BU01QA@SOIC8[150 mil] [DX1045#1]
JS25BU01QA@SOIC8[200 mil] [DX1044#1]
JS25BU01QA@VSOP8 [DX1045#1] JS25BU01QA@WSON8 [DX4005#1]
JS25BU02QA@SOIC8[150 mil] [DX1045#1]
JS25BU02QA@SOIC8[200 mil] [DX1044#1]
JS25BU02QA@VSOP8 [DX1045#1] JS25BU02QA@WSON8 [DX4005#1]
JS25BU04QA@SOIC8[150 mil] [DX1045#1]
JS25BU04QA@SOIC8[200 mil] [DX1044#1]
JS25BU04QA@VSOP8 [DX1045#1] JS25BU04QA@WSON8 [DX4005#1]
JS25BU08QA@SOIC8[150 mil] [DX1045#1]
JS25BU08QA@SOIC8[200 mil] [DX1044#1]
JS25BU08QA@VSOP8 [DX1045#1] JS25BU08QA@WSON8 [DX4005#1]
JS25BU16QA@SOIC8[150 mil] [DX1045#1]
JS25BU16QA@SOIC8[200 mil] [DX1044#1]
JS25BU16QA@VSOP8 [DX1045#1] JS25BU16QA@WSON8 [DX4005#1]
JS25BU32QA@SOIC8[150 mil] [DX1045#1]
JS25BU32QA@SOIC8[200 mil] [DX1044#1]
JS25BU32QA@VSOP8 [DX1045#1] JS25BU32QA@WSON8 [DX4005#1]
JS25BU5KQA@SOIC8[150 mil] [DX1045#1]
JS25BU5KQA@SOIC8[200 mil] [DX1044#1]
JS25BU5KQA@VSOP8 [DX1045#1] JS25BU5KQA@WSON8 [DX4005#1]
JS25P01QA@DFN8 [DX4047#1]
JS25P01QA@SOP8[150 mil] [DX1045#1]
JS25P01QA@SOP8[200 mil] [DX1044#1]
JS25P01QA@VDFN8 [DX4005#1] JS25P01QA@VSOP8 [DX1045#1]
JS25P01QA@VVSOP8 [DX1045#1] JS25P01QA@WSON8 [DX4005#1]
JS25P02QA@DFN8 [DX4047#1]
JS25P02QA@SOP8[150 mil] [DX1045#1]
JS25P02QA@SOP8[200 mil] [DX1044#1]
JS25P02QA@VDFN8 [DX4005#1] JS25P02QA@VSOP8 [DX1045#1]
JS25P02QA@VVSOP8 [DX1045#1] JS25P02QA@WSON8 [DX4005#1]
JS25P04QA@DFN8 [DX4047#1]
JS25P04QA@SOP8[150 mil] [DX1045#1]
JS25P04QA@SOP8[200 mil] [DX1044#1]
JS25P04QA@VDFN8 [DX4005#1] JS25P04QA@VSOP8 [DX1045#1]
JS25P04QA@VVSOP8 [DX1045#1] JS25P04QA@WSON8 [DX4005#1]
JS25P08QA@DFN8 [DX4047#1]
JS25P08QA@SOP8[150 mil] [DX1045#1]
JS25P08QA@SOP8[200 mil] [DX1044#1]
JS25P08QA@VDFN8 [DX4005#1] JS25P08QA@VSOP8 [DX1045#1]
JS25P08QA@VVSOP8 [DX1045#1] JS25P08QA@WSON8 [DX4005#1]

JS25P16QA@DFN8 [DX4047#1]
JS25P16QA@SOP8[150 mil] [DX1045#1]
JS25P16QA@SOP8[200 mil] [DX1044#1]
JS25P16QA@VDFN8 [DX4005#1]
JS25P16QA@VSOP8 [DX1045#1]
JS25P16QA@VVSOP8 [DX1045#1]
JS25P16QA@WSON8 [DX4005#1]
JSFA9A2N72ABB@BGA107 [DX5028]
JSFA9A2N72BBB@BGA107 [DX5028]
JSFA9B2N73BBA@BGA130 [DX5140-1]
JSFA9C2N72ABB@BGA107 [DX5028-1]
JSFA9C2N72BBB@BGA107 [DX5028-1]
JSFA9C2N73BBA@BGA130 [DX5140-1]
JSFA9C2NH3ABB@BGA107 [DX5028]
JSFBAB2N72ABC@BGA137 [DX5011-1]
JSFBAD2N72ABC@BGA137 [DX5011-1]
JSM28323PTAACKZ@FBGA56 [DX5135]
JSM28324ULB1BMA@FBGA56 [DX5045]
JSM64323PTAABKQ@FBGA52 [DX5127]
JSM64323PTAABKZ@FBGA56 [DX5135]
JSM64323PTBABKQ@FBGA52 [DX5127]
JSM64323PTBABKZ@FBGA56 [DX5135]
JSM64323PTBASKQ@FBGA52 [DX5127]
JSM64323PTBASKZ@FBGA52 [DX5135]
JSM64323UB1BMA@FBGA56 [DX5045]
JSM64323UH1BMA@FBGA56 [DX5045]
JSM64323UL1BMA@FBGA56 [DX5045]
JSM64323UT1BMA@FBGA56 [DX5045]
JSM6432TPUA1B6Z@FBGA56 [DX5135#1]

KINGSTON

E(E)PROM/FRAM/NVRAM

KE44A-26BN/4GB@FBGA169 [DX5113]
KE44B-25AN/2G@FBGA153 [DX5104]
KSLCBBL1FB2G3A@FBGA137 [DX5011-1]

K-LINE

E(E)PROM/FRAM/NVRAM

K24C32 [DX0001]
K24C32@SOIC8 [DX1045]
K24C32@TSSOP8 [DX1059]
K24C64 [DX0001]
K24C64@SOIC8 [DX1045]
K24C64@TSSOP8 [DX1059]

KODENSHI

E(E)PROM/FRAM/NVRAM

KK24LC02B [DX0001]
KK24LC02B@SOIC8 [DX1045]
KK24LC04B [DX0001]
KK24LC04B@SOIC8 [DX1045]
KK24LC08B [DX0001]
KK24LC08B@SOIC8 [DX1045]
KK24LC16B [DX0001]
KK24LC16B@SOIC8 [DX1045]

LATTICE

PLD

GAL16LV8 [DX0001]
GAL16LV8C [DX0001]
GAL16LV8D [DX0001]
GAL16LV8Z [DX0001]
GAL16LV8ZD [DX0001]
GAL16V8 [DX0001]
GAL16V8@SOIC20 [DX1033]
GAL16V8A@PLCC20 [DX2020]
GAL16V8B [DX0001]
GAL16V8B@SOIC20 [DX1033]
GAL16V8C@PLCC20 [DX2020]
GAL16V8D [DX0001]
GAL16V8D@SOIC20 [DX1033]
GAL16V8Z@PLCC20 [DX2020]
GAL16VP8 [DX0001]
GAL16VP8B [DX0001]
GAL18V10 [DX0001]
GAL18V10B [DX0001]
GAL20LV8 [DX0001]
GAL20LV8Z [DX0001]
GAL20LV8ZD [DX0001]
GAL20RA10 [DX0001]
GAL20RA10B [DX0001]
GAL20V8 [DX0001]
GAL20V8A [DX0001]
GAL20V8B [DX0001]
GAL20V8C [DX0001]
GAL20V8Z [DX0001]
GAL20XV10 [DX0001]
GAL20XV10B [DX0001]
GAL22V10 [DX0001]
GAL22V10@SOIC24 [DX1033]
GAL22V10A@PLCC28 [DX2028]
GAL22V10B [DX0001]
GAL22V10B@SOIC24 [DX1033]
GAL22V10BQ@PLCC28 [DX2028]
GAL22V10C [DX0001]
GAL22V10C@SOIC24 [DX1033]
GAL22V10D@PLCC28 [DX2028]
GAL26CLV12 [DX0001]
GAL26CLV12@SOIC28 [DX1033]
GAL26CLV12B [DX0001]
GAL26CLV12B@SOIC28 [DX1033]
GAL26CLV12C [DX0001]
GAL26CLV12C@SOIC28 [DX1033]
GAL26CLV12D [DX0001]
GAL26CLV12D@SOIC28 [DX1033]
GAL16LV8@PLCC20 [DX2020]
GAL16LV8C@PLCC20 [DX2020]
GAL16LV8D@PLCC20 [DX2020]
GAL16LV8Z@PLCC20 [DX2020]
GAL16LV8ZD@PLCC20 [DX2020]
GAL16V8@PLCC20 [DX2020]
GAL16V8A [DX0001]
GAL16V8A@SOIC20 [DX1033]
GAL16V8B@PLCC20 [DX2020]
GAL16V8C [DX0001]
GAL16V8C@SOIC20 [DX1033]
GAL16V8D@PLCC20 [DX2020]
GAL16V8Z [DX0001]
GAL16V8Z@SOIC20 [DX1033]
GAL16VP8@PLCC20 [DX2020]
GAL16VP8B@PLCC20 [DX2020]
GAL18V10@PLCC20 [DX2020]
GAL18V10B@PLCC20 [DX2020]
GAL20LV8@PLCC28 [DX2028]
GAL20LV8Z@PLCC28 [DX2028]
GAL20LV8ZD@PLCC28 [DX2028]
GAL20RA10@PLCC28 [DX2028]
GAL20RA10B@PLCC28 [DX2028]
GAL20V8@PLCC28 [DX2028]
GAL20V8A@PLCC28 [DX2028]
GAL20V8B@PLCC28 [DX2028]
GAL20V8C@PLCC28 [DX2028]
GAL20V8Z@PLCC28 [DX2028]
GAL20XV10@PLCC28 [DX2028]
GAL20XV10B@PLCC28 [DX2028]
GAL22V10@PLCC28 [DX2028]
GAL22V10A [DX0001]
GAL22V10A@SOIC24 [DX1033]
GAL22V10B@PLCC28 [DX2028]
GAL22V10BQ [DX0001]
GAL22V10BQ@SOIC24 [DX1033]
GAL22V10C@PLCC28 [DX2028]
GAL22V10D [DX0001]
GAL22V10D@SOIC24 [DX1033]
GAL26CLV12@PLCC28 [DX2028]
GAL26CLV12@TSOP28 [DX1001]
GAL26CLV12B@PLCC28 [DX2028]
GAL26CLV12B@TSOP28 [DX1001]
GAL26CLV12C@PLCC28 [DX2028]
GAL26CLV12C@TSOP28 [DX1001]
GAL26CLV12D@PLCC28 [DX2028]
GAL26CLV12D@TSOP28 [DX1001]

GAL26CLV12Z [DX0001]
GAL26CLV12Z@PLCC28 [DX2028]
GAL26CLV12Z@SOIC28 [DX1033]
GAL26CLV12Z@TSOP28 [DX1001]
GAL26CLV12ZD [DX0001]
GAL26CLV12ZD@PLCC28 [DX2028]
GAL26CLV12ZD@SOIC28 [DX1033]
GAL26CLV12ZD@TSOP28 [DX1001]
GAL26CV12 [DX0001]
GAL26CV12@PLCC28 [DX2028]
GAL26CV12B [DX0001]
GAL26CV12B@PLCC28 [DX2028]
GAL26CV12C [DX0001]
GAL26CV12C@PLCC28 [DX2028]
GAL26V12C [DX0001]
GAL26V12C@PLCC28 [DX2028]
GAL6001B [DX0001]
GAL6001B@PLCC28 [DX2028]
GAL6002B [DX0001]
GAL6002B@PLCC28 [DX2028]
iM4A3-192/96@VQFP144 [DX3035]
iM4A5-192/96@VQFP144 [DX3035]
isp2128VE@caBGA100 [DX5106]
isp2128VE@PLCC84 [DX2084]
isp2128VE@TQFP100 [DX3021]
ispGAL22LV10 [DX0001]
ispGAL22LV10@PLCC28 [DX2028]
ispGAL22LV10@SSOP28 [DX1026]
ispGAL22LV10A [DX0001]
ispGAL22LV10A@PLCC28 [DX2028]
ispGAL22LV10A@SSOP28 [DX1026]
ispGAL22LV10B [DX0001]
ispGAL22LV10B@PLCC28 [DX2028]
ispGAL22LV10B@SSOP28 [DX1026]
ispGAL22LV10C [DX0001]
ispGAL22LV10C@PLCC28 [DX2028]
ispGAL22LV10C@SSOP28 [DX1026]
ispGAL22LV10D [DX0001]
ispGAL22LV10D@PLCC28 [DX2028]
ispGAL22LV10D@SSOP28 [DX1026]
ispGAL22V10AB@PLCC28 [DX2028]
ispGAL22V10AB@QFN32 [DX4015]
ispGAL22V10AC@PLCC28 [DX2028]
ispGAL22V10AC@QFN32 [DX4015]
ispGAL22V10AV@PLCC28 [DX2028]
ispGAL22V10AV@QFN32 [DX4015]
ispGAL22V10AZC@PLCC28 [DX2028]
ispGAL22V10AZC@QFN32 [DX4015]
ispGAL22V10C(UES)@PLCC28 [DX2028]
ispGAL22V10C(UES)@SSOP28 [DX1026]
ispGAL22V10C@PLCC28 [DX2028]
ispGAL22V10C@SSOP28 [DX1026]
ispGDX80VA@TQFP100 [DX3021]
ispLSI1016@PLCC44 [DX2044]
ispLSI1016@TQFP44 [DX3003]
ispLSI1016E@PLCC44 [DX2044]
ispLSI1016E@TQFP44 [DX3003]
ispLSI1016EA@PLCC44 [DX2044]
ispLSI1016EA@TQFP44 [DX3003]
ispLSI1024@PLCC68 [DX2068]
ispLSI1024E@PLCC68 [DX2068]
ispLSI1032@CPGA84 [DX5000]
ispLSI1032@PLCC84 [DX2084]
ispLSI1032@TQFP100 [DX3021]
ispLSI1032E@CPGA84 [DX5000]
ispLSI1032E@PLCC84 [DX2084]
ispLSI1032E@TQFP100 [DX3021]
ispLSI1048C@PQFP128 [DX3033]
ispLSI1048C@TQFP128 [DX3030]
ispLSI1048E@PQFP128 [DX3033]
ispLSI1048E@TQFP128 [DX3030]
ispLSI2032@PLCC44 [DX2044]
ispLSI2032@TQFP44 [DX3003]
ispLSI2032A@PLCC44 [DX2044]
ispLSI2032A@TQFP44 [DX3003]
ispLSI2032A@TQFP48 [DX3007]
ispLSI2032E@PLCC44 [DX2044]
ispLSI2032E@TQFP44 [DX3003]
ispLSI2032E@TQFP48 [DX3007]
ispLSI2032V@PLCC44 [DX2044]
ispLSI2032V@TQFP44 [DX3003]
ispLSI2032V@TQFP48 [DX3007]
ispLSI2032VE@PLCC44 [DX2044]
ispLSI2032VE@TQFP44 [DX3003]
ispLSI2032VE@TQFP48 [DX3007]
ispLSI2064@CPGA84 [DX5000]
ispLSI2064@PLCC84 [DX2084]
ispLSI2064@TQFP100 [DX3021]
ispLSI2064A@PLCC44 [DX2044]
ispLSI2064A@PLCC84 [DX2084]
ispLSI2064A@TQFP100 [DX3021]
ispLSI2064A@TQFP44 [DX3003]
ispLSI2064E@PQFP100 [DX3022]
ispLSI2064E@TQFP100 [DX3021]

ispLSI2064V@PLCC44 [DX2044]
ispLSI2064V@PLCC84 [DX2084]
ispLSI2064V@TQFP100 [DX3021]
ispLSI2064V@TQFP44 [DX3003]
ispLSI2064VE@CBGA100 [DX5106]
ispLSI2064VE@PLCC44 [DX2044]
ispLSI2064VE@TQFP100 [DX3021]
ispLSI2064VE@TQFP44 [DX3003]
ispLSI2096A@PQFP128 [DX3033]
ispLSI2096A@TQFP128 [DX3030]
ispLSI2096E@TQFP128(ISP) [DX3030]
ispLSI2096VE@TQFP128(ISP) [DX3030]
ispLSI2128A@PLCC84 [DX2084]
ispLSI2128A@TQFP100 [DX3021]
ispLSI2128V@PLCC84 [DX2084]
ispLSI2128V@TQFP100 [DX3021]
ispLSI2128VE@caBGA100 [DX5106]
ispLSI2128VE@PLCC84 [DX2084]
ispLSI2128VE@TQFP100 [DX3021]
ispLSI2192VE@TQFP128 [DX3030]
ispPAC-CLK5304S@TQFP48 [DX3047]
ispPAC-CLK5308S@TQFP48 [DX3047]
ispPAC-CLK5312S@TQFP48 [DX3047]
ispPAC-CLK5316S@TQFP64 [DX3011]
ispPAC-CLK5320S@TQFP64 [DX3011]
ispPAC-CLK5406D@QFNS48 [DX4021]
ispPAC-CLK5410D@QFNS64 [DX4023]
ispPAC-CLK5510V@TQFP48 [DX3047]
ispPAC-CLK5520V@TQFP100 [DX3021]
ispPAC-CLK5610AV@TQFP48 [DX3047]
ispPAC-CLK5610V@TQFP48 [DX3047]
ispPAC-CLK5620AV@TQFP100 [DX3021]
ispPAC-CLK5620V@TQFP100 [DX3021]
ispPAC-POWR1014@TQFP48 [DX3007]
ispPAC-POWR1014A@TQFP48 [DX3007]
ispPAC-POWR1208@TQFP44 [DX3005]
ispPAC-POWR1208P1@TQFP44 [DX3005]
ispPAC-POWR1220AT8@TQFP100 [DX3043]
ispPAC-POWR604@TQFP44 [DX3005]
ispPAC-POWR605@QFN24 [DX4034]
ispPAC-POWR607@QFN32 [DX4015]
ispPAC-POWR6AT6@QFN32 [DX4015]
LC4032B@TQFP44 [DX3003]
LC4032B@TQFP48 [DX3007]
LC4032C@TQFP44 [DX3003]
LC4032C@TQFP48 [DX3007]
LC4032V@TQFP44 [DX3003]
LC4032V@TQFP48 [DX3007]
LC4032ZC@TQFP48 [DX3007]
LC4032ZE@TQFP48 [DX3007]
LC4064B@TQFP100 [DX3021]
LC4064B@TQFP44 [DX3003]
LC4064B@TQFP48 [DX3007]
LC4064C@TQFP100 [DX3021]
LC4064C@TQFP44 [DX3003]
LC4064C@TQFP48 [DX3007]
LC4064V@TQFP100 [DX3021]
LC4064V@TQFP44 [DX3003]
LC4064V@TQFP48 [DX3007]
LC4064ZC@TQFP100 [DX3021]
LC4064ZC@TQFP48 [DX3007]
LC4064ZE@csBGA144 [DX5220]
LC4064ZE@TQFP100 [DX3021]
LC4064ZE@TQFP48 [DX3007]
LC4128B@TQFP100 [DX3021]
LC4128B@TQFP128 [DX3030]
LC4128B@TQFP144 [DX3035]
LC4128C@TQFP100 [DX3021]
LC4128C@TQFP128 [DX3030]
LC4128C@TQFP144 [DX3035]
LC4128V@TQFP100 [DX3021]
LC4128V@TQFP128 [DX3030]
LC4128V@TQFP144 [DX3035]
LC4128ZC@TQFP100 [DX3021]
LC4128ZC@TQFP128 [DX3030]
LC4128ZC@TQFP144 [DX3035]
LC4128ZE@CSBGA144 [DX5220]
LC4128ZE@TQFP100 [DX3021]
LC4128ZE@TQFP144 [DX3035]
LC4256B(128I/O)@FBGA256A [DX5225]
LC4256B(160I/O)@FBGA256B [DX5225]
LC4256B@TQFP100 [DX3021]
LC4256B@TQFP176(*) [DX3086]
LC4256C(128I/O)@FBGA256A [DX5225]
LC4256C(160I/O)@FBGA256B [DX5225]

LC4256C@TQFP100 [DX3021]
LC4256C@TQFP176(*) [DX3086]
LC4256V(128I/O)@FBGA256A [DX5225]
LC4256V(160I/O)@FBGA256B [DX5225]
LC4256V@TQFP100 [DX3021]
LC4256V@TQFP144 [DX3035]
LC4256V@TQFP144(R90) [DX3035]
LC4256V@TQFP176(*) [DX3086]
LC4256ZC@TQFP100 [DX3021]
LC4256ZC@TQFP176(*) [DX3086]
LC4256ZE@csBGA144 [DX5220]
LC4256ZE@TQFP100 [DX3021]
LC4256ZE@TQFP144 [DX3035]
LC4384B@FBGA256 [DX5225]
LC4384B@TQFP176(*) [DX3086]
LC4384C@FBGA256 [DX5225]
LC4384C@TQFP176(*) [DX3086]
LC4384V@FBGA256 [DX5225]
LC4384V@TQFP176(*) [DX3086]
LC4512B@FBGA256 [DX5225]
LC4512B@TQFP176(*) [DX3086]
LC4512C@FBGA256 [DX5225]
LC4512C@TQFP176(*) [DX3086]
LC4512V@FBGA256 [DX5225]
LC4512V@TQFP176(*) [DX3086]
LC5256MB@FBGA256 [DX5201]
LC5256MC@FBGA256 [DX5201]
LC5256MV@FBGA256 [DX5201]
LCMXO1200C_3F256 [DX5160]
LCMXO1200C_3M132 [DX5069]
LCMXO1200C_3T100 [DX3021]
LCMXO1200C_3T144 [DX3051]
LCMXO1200C_4F256 [DX5160]
LCMXO1200C_4M132 [DX5069]
LCMXO1200C_4T100 [DX3021]
LCMXO1200C_4T144 [DX3051]
LCMXO1200C_5F256 [DX5160]
LCMXO1200C_5M132 [DX5069]
LCMXO1200C_5T100 [DX3021]
LCMXO1200C_5T144 [DX3051]
LCMXO2-1200HC@csBGA132 [DX5069]
LCMXO2-1200HC@TQFP100 [DX3021]
LCMXO2-1200HC@TQFP144 [DX3051]
LCMXO2-2000HC@csBGA132 [DX5069]
LCMXO2-2000HC@TQFP100 [DX3021]
LCMXO2-256HC@QFN32 [DX4015]
LCMXO2-256HC@TQFP100 [DX3021]
LCMXO2280C_3F256 [DX5160]
LCMXO2280C_3M132 [DX5069]
LCMXO2280C_3T100 [DX3021]
LCMXO2280C_3T144 [DX3051]
LCMXO2280C_4F256 [DX5160]
LCMXO2280C_4M132 [DX5069]
LCMXO2280C_4T100 [DX3021]
LCMXO2280C_4T144 [DX3035]
LCMXO2280C_5F256 [DX5160]
LCMXO2280C_5M132 [DX5069]
LCMXO2280C_5T100 [DX3021]
LCMXO2280C_5T144 [DX3051]
LCMXO2-4000HC@csBGA132 [DX5069]
LCMXO2-4000HC@TQFP144 [DX3051]
LCMXO256C-3M100 [DX5069]
LCMXO256C-3T100 [DX3021]
LCMXO256C-4M100 [DX5069]
LCMXO256C-4T100 [DX3021]
LCMXO256C-5M100 [DX5069]
LCMXO256C-5T100 [DX3021]
LCMXO2-640HC@TQFP100 [DX3021]
LCMXO2-640UHC@TQFP144 [DX3035]
LCMXO2-7000HC@TQFP144 [DX3051]
LCMXO640C_3F256 [DX5160]
LCMXO640C_3FT256 [DX5160]
LCMXO640C_3M100 [DX5069]
LCMXO640C_3M132 [DX5069]
LCMXO640C_3T100 [DX3021]
LCMXO640C_3T144 [DX3051]
LCMXO640C_4F256 [DX5160]
LCMXO640C_4FT256 [DX5160]
LCMXO640C_4M100 [DX5069]
LCMXO640C_4M132 [DX5069]
LCMXO640C_4T100 [DX3021]
LCMXO640C_4T144 [DX3051]
LCMXO640C_5F256 [DX5160]
LCMXO640C_5FT256 [DX5160]
LCMXO640C_5M100 [DX5069]
LCMXO640C_5M132 [DX5069]
LCMXO640C_5T100 [DX3021]
LCMXO640C_5T144 [DX3051]
LFXP10C-3F256(ISP) [DX0001]
LFXP10C-3F388(ISP) [DX0001]
LFXP10C-4F256(ISP) [DX0001]
LFXP10C-4F388(ISP) [DX0001]
LFXP10C-5F256(ISP) [DX0001]
LFXP10C-5F388(ISP) [DX0001]

LFXP10E-3F256(ISP) [DX0001]
LFXP10E-3F388(ISP) [DX0001]
LFXP10E-4F256(ISP) [DX0001]
LFXP10E-4F388(ISP) [DX0001]
LFXP10E-5F256(ISP) [DX0001]
LFXP10E-5F388(ISP) [DX0001]
LFXP15C-3F256(ISP) [DX0001]
LFXP15C-3F388(ISP) [DX0001]
LFXP15C-3F484(ISP) [DX0001]
LFXP15C-4F256(ISP) [DX0001]
LFXP15C-4F388(ISP) [DX0001]
LFXP15C-4F484(ISP) [DX0001]
LFXP15C-5F256(ISP) [DX0001]
LFXP15C-5F388(ISP) [DX0001]
LFXP15C-5F484(ISP) [DX0001]
LFXP15E-3F256(ISP) [DX0001]
LFXP15E-3F388(ISP) [DX0001]
LFXP15E-3F484(ISP) [DX0001]
LFXP15E-4F256(ISP) [DX0001]
LFXP15E-4F388(ISP) [DX0001]
LFXP15E-4F484(ISP) [DX0001]
LFXP15E-5F256(ISP) [DX0001]
LFXP15E-5F388(ISP) [DX0001]
LFXP15E-5F484(ISP) [DX0001]
LFXP2_17E_5FN484(ISP) [DX0001]
LFXP2_17E_5FTN256(ISP) [DX0001]
LFXP2_17E_5QN208(ISP) [DX0001]
LFXP2_17E_6FN484(ISP) [DX0001]
LFXP2_17E_6FTN256(ISP) [DX0001]
LFXP2_17E_6QN208(ISP) [DX0001]
LFXP2_17E_7FN484(ISP) [DX0001]
LFXP2_17E_7FTN256(ISP) [DX0001]
LFXP2_17E_7QN208(ISP) [DX0001]
LFXP2_30E_5F484(ISP) [DX0001]
LFXP2_30E_5F672(ISP) [DX0001]
LFXP2_30E_5FTN256(ISP) [DX0001]
LFXP2_30E_6F484(ISP) [DX0001]
LFXP2_30E_6F672(ISP) [DX0001]
LFXP2_30E_6FTN256(ISP) [DX0001]
LFXP2_30E_7F484(ISP) [DX0001]
LFXP2_30E_7F672(ISP) [DX0001]
LFXP2_30E_7FTN256(ISP) [DX0001]
LFXP2_40E_5FN484(ISP) [DX0001]
LFXP2_40E_5FN672(ISP) [DX0001]
LFXP2_40E_6FN484(ISP) [DX0001]
LFXP2_40E_6FN672(ISP) [DX0001]
LFXP2_40E_7FN484(ISP) [DX0001]
LFXP2_40E_7FN672(ISP) [DX0001]
LFXP2_5E_5MN132 [DX5069]
LFXP2_5E_5TN144 [DX3051]
LFXP2_5E_6MN132 [DX5069]
LFXP2_5E_6TN144 [DX3051]
LFXP2_5E_7MN132 [DX5069]
LFXP2_5E_7TN144 [DX3051]
LFXP20C-3F256(ISP) [DX0001]
LFXP20C-3F388(ISP) [DX0001]
LFXP20C-3F484(ISP) [DX0001]
LFXP20C-4F256(ISP) [DX0001]
LFXP20C-4F388(ISP) [DX0001]
LFXP20C-4F484(ISP) [DX0001]
LFXP20C-5F256(ISP) [DX0001]
LFXP20C-5F388(ISP) [DX0001]
LFXP20C-5F484(ISP) [DX0001]
LFXP20E-3F256(ISP) [DX0001]
LFXP20E-3F388(ISP) [DX0001]
LFXP20E-3F484(ISP) [DX0001]
LFXP20E-4F256(ISP) [DX0001]
LFXP20E-4F388(ISP) [DX0001]
LFXP20E-4F484(ISP) [DX0001]
LFXP20E-5F256(ISP) [DX0001]
LFXP20E-5F388(ISP) [DX0001]
LFXP20E-5F484(ISP) [DX0001]
LFXP3C@TQFP100 [DX3021]
LFXP3C@TQFP144 [DX3035]
LFXP3E@TQFP100 [DX3021]
LFXP3E@TQFP144 [DX3035]
LFXP6C@TQFP144 [DX3035]
LFXP6E@TQFP144 [DX3035]
LX128B(EB)@FBGA208
LX128B-2R@FBGA208
LX128C(EC)@FBGA208
LX128C-2R@FBGA208
LX128V(EV)@FBGA208
LX128V-2R@FBGA208
LX256B(EB)@FBGA484
LX256B-2R@FBGA484
LX256C(EC)@FBGA484
LX256C-2R@FBGA484
LX256V(EV)@FBGA484
LX256V-2R@FBGA484
LX64B(EB)@FBGA100 [DX5059]
LX64B-2R@FBGA100 [DX5059]
LX64C(EC)@FBGA100 [DX5059]
LX64C-2R@FBGA100 [DX5059]
LX64V(EV)@FBGA100 [DX5059]
LX64V-2R@FBGA100 [DX5059]

M4-128/64@PQFP100 [DX3022]
M4-128/64@TQFP100 [DX3021]
M4-128N/64@PLCC84 [DX2084]
M4-192/96@VQFP144 [DX3035]
M4-32/32@PLCC44 [DX2044]
M4-32/32@TQFP44 [DX3003]
M4-32/32@TQFP48 [DX3007]
M4-64/32@PLCC44 [DX2044]
M4-64/32@TQFP44 [DX3003]
M4-64/32@TQFP48 [DX3007]
M4-96/48@TQFP100 [DX3021]
M4A3-128/64@PQFP100 [DX3022]
M4A3-128/64@TQFP100 [DX3021]
M4A3-128N/64@PLCC84 [DX2084]
M4A3-32/32@PLCC44 [DX2044]
M4A3-32/32@TQFP44 [DX3003]
M4A3-32/32@TQFP48 [DX3007]
M4A3-384-160 [DX3118]
M4A3-384-192 [DX0001]
M4A3-512-160 [DX3118]
M4A3-512-192 [DX0001]
M4A3-512-256 [DX0001]
M4A3-64/32@PLCC44 [DX2044]
M4A3-64/32@TQFP44 [DX3003]
M4A3-64/32@TQFP48 [DX3007]
M4A3-64/64@TQFP100 [DX3021]
M4A3-96/48@TQFP100 [DX3021]
M4A5-128/64@PQFP100 [DX3022]
M4A5-128/64@TQFP100 [DX3021]
M4A5-128N/64@PLCC84 [DX2084]
M4A5-32/32@PLCC44 [DX2044]
M4A5-32/32@TQFP44 [DX3003]
M4A5-32/32@TQFP48 [DX3007]
M4A5-64/32@PLCC44 [DX2044]
M4A5-64/32@TQFP44 [DX3003]
M4A5-64/32@TQFP48 [DX3007]
M4A5-96/48@TQFP100 [DX3021]
M4LV-128/64@PQFP100 [DX3022]
M4LV-128/64@TQFP100 [DX3021]
M4LV-128N/64@PLCC84 [DX2084]
M4LV-32/32@PLCC44 [DX2044]
M4LV-32/32@TQFP44 [DX3003]
M4LV-32/32@TQFP48 [DX3007]
M4LV-64/32@PLCC44 [DX2044]
M4LV-64/32@TQFP44 [DX3003]
M4LV-64/32@TQFP48 [DX3007]
M4LV-96/48@TQFP100 [DX3021]
MACH110@PLCC44 [DX2044]
MACH111@PLCC44 [DX2044]
MACH111@TQFP44 [DX3003]
MACH120@PLCC68 [DX2068]
MACH130@PLCC84 [DX2084]
MACH131/1@PLCC84 [DX2084]
MACH131@PLCC84 [DX2084]
MACH131SP@PQFP100 [DX3022]
MACH131SP@TQFP100 [DX3021]
MACH210@PLCC44 [DX2044]
MACH210@TQFP44 [DX3003]
MACH210A@PLCC44 [DX2044]
MACH210A@TQFP44 [DX3003]
MACH210AQ@PLCC44 [DX2044]
MACH210AQ@TQFP44 [DX3003]
MACH211@PLCC44 [DX2044]
MACH220@PLCC68 [DX2068]
MACH221@PLCC68 [DX2068]
MACH231SP@PLCC84 [DX2084]
MACH231SP@PQFP100 [DX3022]
MACH231SP@TQFP100 [DX3021]
MACH435@PLCC84 [DX2084]
MACH436@PLCC84 [DX2084]
MACH446@PQFP100 [DX3022]
MACH446@TQFP100 [DX3021]
MACHLV210@PLCC44 [DX2044]
MACHLV210@TQFP44 [DX3003]
MACHLV436@PLCC84 [DX2084]
MACHLV446@PQFP100 [DX3022]
MACHLV446@TQFP100 [DX3021]
PAL29M16H [DX0001]
PALCE20RA10 [DX0001]
PALCE20RA10@PLCC28 [DX2028]
PALCE20RA10@SOIC24 [DX1033]
PALCE20RA10H [DX0001]
PALCE20RA10H@PLCC28 [DX2028]
PALCE20RA10H@SOIC24 [DX1033]
PALCE20RA10Q [DX0001]
PALCE20RA10Q@PLCC28 [DX2028]
PALCE20RA10Q@SOIC24 [DX1033]
PALCE22V10H [DX0001]
PALCE22V10H@PLCC28 [DX2028]
PALCE22V10H@SOIC24 [DX1003]
PALCE22V10Q [DX0001]
PALCE22V10Q@PLCC28 [DX2028]
PALCE22V10Q@SOIC24 [DX1003]
PALCE22V10Z [DX0001]
PALCE22V10Z@PLCC28 [DX2028]
PALCE22V10Z@SOIC24 [DX1003]

PALCE26V12H/4 [DX0001]
PALCE26V12H/4@PLCC28 [DX2028]
PALCE26V12H/4@SOIC28 [DX1033]
PALCE26V12H-15 [DX0001]
PALCE26V12H-15@PLCC28 [DX2028]
PALCE26V12H-15@SOIC28 [DX1033]
PALCE26V12H-20 [DX0001]
PALCE26V12H-20@PLCC28 [DX2028]
PALCE26V12H-20@SOIC28 [DX1033]
PALCE26V12H-25 [DX0001]
PALCE26V12H-25@PLCC28 [DX2028]
PALCE26V12H-25@SOIC28 [DX1033]
PALCE29M16H [DX0001]
PALCE29M16H@PLCC28 [DX2028]
PALCE29M16H@SOIC24 [DX1033]
PALCE29MA16H [DX0001]
PALCE29MA16H@PLCC28 [DX2028]
PALCE29MA16H@SOIC24 [DX1033]
PALCE610 [DX0001]
PALCE610@PLCC28 [DX2028]
PALCE610@SOIC24 [DX1003]
PALCE610H [DX0001]
PALCE610H@PLCC28 [DX2028]
PALCE610H@SOIC24 [DX1003]
PALCE630H [DX0001]
PALCE630H@PLCC28 [DX2028]
PALCE630H@SOIC24 [DX1003]
XP2_8E_5MN132 [DX5069]
XP2_8E_5TN144 [DX3051]
XP2_8E_6MN132 [DX5069]
XP2_8E_6TN144 [DX3051]
XP2_8E_7MN132 [DX5069]
XP2_8E_7TN144 [DX3051]

LEAHKIINN

E(E)PROM/FRAM/NVRAM

KTR0403AS@FBGA137 [DX5011-1]

LEAHKINN

E(E)PROM/FRAM/NVRAM

KPR0405FS@BGA168 [DX5205]
KTR0405AS@BGA137 [DX5011-1]
KVR0302AS@BGA130 [DX5011-1]

LG

MICROCONTROLLER

R5F1006AASP [DX1026]
R5F1006ADSP [DX1026]
R5F1006CASP [DX1026]
R5F1006CDSP [DX1026]
R5F1006DASP [DX1026]
R5F1006DDSP [DX1026]
R5F1006EASP [DX1026]
R5F1006EDSP [DX1026]
R5F1006FASP [DX1026]
R5F1006FDSP [DX1026]
R5F1006GASP [DX1026]
R5F1006GDSP [DX1026]
R5F1006HASP [DX1026]
R5F1006HDSP [DX1026]
R5F1006JASP [DX1026]
R5F1006JDSP [DX1026]
R5F1006KASP [DX1026]
R5F1006KDSP [DX1026]
R5F1006LASP [DX1026]
R5F1006LDSP [DX1026]

R5F1007AANA [DX4012]
R5F1007ADNA [DX4012]
R5F1007CANA [DX4012]
R5F1007CDNA [DX4012]
R5F1007DANA [DX4012]
R5F1007DDNA [DX4012]
R5F1007EANA [DX4012]
R5F1007EDNA [DX4012]
R5F1007FANA [DX4012]
R5F1007FDNA [DX4012]
R5F1007GANA [DX4012]
R5F1007GDNA [DX4012]
R5F1007HANA [DX4012]
R5F1007HDNA [DX4012]
R5F1007JANA [DX4012]
R5F1007JDNA [DX4012]
R5F1007KANA [DX4012]
R5F1007KDNA [DX4012]
R5F1007LANA [DX4012]
R5F1007LDNA [DX4012]
R5F1008AALA [DX0001]
R5F1008ADLA [DX0001]
R5F1008CALA [DX0001]
R5F1008CDLA [DX0001]
R5F1008DALA [DX0001]
R5F1008DDLA [DX0001]
R5F1008EALA [DX0001]
R5F1008EDLA [DX0001]
R5F1008FALA [DX0001]
R5F1008FDLA [DX0001]
R5F1008GALA [DX0001]
R5F1008GDLA [DX0001]
R5F1008HALA [DX0001]
R5F1008HDLA [DX0001]
R5F1008JALA [DX0001]
R5F1008JDLA [DX0001]
R5F1008KALA [DX0001]
R5F1008KDLA [DX0001]
R5F1008LALA [DX0001]
R5F1008LDLA [DX0001]
R5F100AAASP [DX1026]
R5F100AADSP [DX1026]
R5F100ACASP [DX1026]
R5F100ACDSP [DX1026]
R5F100ADASP [DX1026]
R5F100ADDSP [DX1026]
R5F100AEASP [DX1026]
R5F100AEDSP [DX1026]
R5F100AFASP [DX1026]
R5F100AFDSP [DX1026]
R5F100AGASP [DX1026]
R5F100AGDSP [DX1026]
R5F100AHASP [DX1026]
R5F100AHDSP [DX1026]
R5F100AJASP [DX1026]
R5F100AJDSP [DX1026]
R5F100AKASP [DX1026]
R5F100AKDSP [DX1026]
R5F100ALASP [DX1026]
R5F100ALDSP [DX1026]
R5F100BAANA [DX4015]
R5F100BADNA [DX4015]
R5F100BCANA [DX4015]
R5F100BCDNA [DX4015]
R5F100BDANA [DX4015]
R5F100BDDNA [DX4015]
R5F100BEANA [DX4015]
R5F100BEDNA [DX4015]
R5F100BFANA [DX4015]
R5F100BFDNA [DX4015]
R5F100BGANA [DX4015]
R5F100BGDNA [DX4015]
R5F100BHANA [DX4015]
R5F100BHDNA [DX4015]
R5F100BJANA [DX4015]
R5F100BJDNA [DX4015]
R5F100BKANA [DX4015]
R5F100BKDNA [DX4015]
R5F100BLANA [DX4015]
R5F100BLDNA [DX4015]
R5F100CAALA [DX0001]
R5F100CADLA [DX0001]
R5F100CCALA [DX0001]
R5F100CCDLA [DX0001]
R5F100CDALA [DX0001]
R5F100CDDLA [DX0001]
R5F100CEALA [DX0001]
R5F100CEDLA [DX0001]
R5F100CFALA [DX0001]
R5F100CFDLA [DX0001]
R5F100CGALA [DX0001]
R5F100CGDLA [DX0001]
R5F100CHALA [DX0001]
R5F100CHDLA [DX0001]
R5F100CJALA [DX0001]
R5F100CJDLA [DX0001]

R5F100CKALA [DX0001]
R5F100CKDLA [DX0001]
R5F100CLALA [DX0001]
R5F100CLDLA [DX0001]
R5F100EAANA [DX4017]
R5F100EADNA [DX4017]
R5F100ECANA [DX4017]
R5F100ECDNA [DX4017]
R5F100EDANA [DX4017]
R5F100EDDNA [DX4017]
R5F100EEANA [DX4017]
R5F100EEDNA [DX4017]
R5F100EFANA [DX4017]
R5F100EFDNA [DX4017]
R5F100EGANA [DX4017]
R5F100EGDNA [DX4017]
R5F100EHANA [DX4017]
R5F100EHDNA [DX4017]
R5F100EJANA [DX4017]
R5F100EJDNA [DX4017]
R5F100EKANA [DX4017]
R5F100EKDNA [DX4017]
R5F100ELANA [DX4017]
R5F100ELDNA [DX4017]
R5F100FAAFP [DX3005]
R5F100FADFP [DX3005]
R5F100FCAFP [DX3005]
R5F100FCDFP [DX3005]
R5F100FDAFP [DX3005]
R5F100FDDFP [DX3005]
R5F100FEAFP [DX3005]
R5F100FEDFP [DX3005]
R5F100FFAFP [DX3005]
R5F100FFDFP [DX3005]
R5F100FGAFP [DX3005]
R5F100FGDFP [DX3005]
R5F100FHAFP [DX3005]
R5F100FHDFP [DX3005]
R5F100FJAFP [DX3005]
R5F100FJDFP [DX3005]
R5F100FKAFP [DX3005]
R5F100FKDFP [DX3005]
R5F100FLAFP [DX3005]
R5F100FLDFP [DX3005]
R5F100GAAFB [DX3007]
R5F100GAANA [DX4021]
R5F100GADFB [DX3007]
R5F100GADNA [DX4021]
R5F100GCAFB [DX3007]
R5F100GCANA [DX4021]
R5F100GCDFB [DX3007]
R5F100GCDNA [DX4021]
R5F100GDAFB [DX3007]
R5F100GDANA [DX4021]
R5F100GDDFB [DX3007]
R5F100GDDNA [DX4021]
R5F100GEAFB [DX3007]
R5F100GEANA [DX4021]
R5F100GEDFB [DX3007]
R5F100GEDNA [DX4021]
R5F100GFAFB [DX3007]
R5F100GFANA [DX4021]
R5F100GFDFB [DX3007]
R5F100GFDNA [DX4021]
R5F100GGAFB [DX3007]
R5F100GGANA [DX4021]
R5F100GGDFB [DX3007]
R5F100GGDNA [DX4021]
R5F100GHAFB [DX3007]
R5F100GHANA [DX4021]
R5F100GHDFB [DX3007]
R5F100GHDNA [DX4021]
R5F100GJAFB [DX3007]
R5F100GJANA [DX4021]
R5F100GJDFB [DX3007]
R5F100GJDNA [DX4021]
R5F100GKAFB [DX3007]
R5F100GKANA [DX4021]
R5F100GKDFB [DX3007]
R5F100GKDNA [DX4021]
R5F100GLAFB [DX3007]
R5F100GLANA [DX4021]
R5F100GLDFB [DX3007]
R5F100GLDNA [DX4021]
R5F100JCAFA [DX3010]
R5F100JCDFA [DX3010]
R5F100JDAFA [DX3010]
R5F100JDDFA [DX3010]
R5F100JEAFA [DX3010]
R5F100JEDFA [DX3010]
R5F100JFAFA [DX3010]
R5F100JFDFA [DX3010]
R5F100JGAFA [DX3010]
R5F100JGDFA [DX3010]
R5F100JHAFA [DX3010]
R5F100JHDFA [DX3010]

R5F100JJAFA [DX3010]
R5F100JJDFA [DX3010]
R5F100JKAFA [DX3010]
R5F100JKDFA [DX3010]
R5F100JLAFA [DX3010]
R5F100JLDFA [DX3010]
R5F100LCABG [DX0001]
R5F100LCAFA [DX3012]
R5F100LCAFB [DX3011]
R5F100LCAFC [DX3085]
R5F100LCDBG [DX0001]
R5F100LCDFA [DX3012]
R5F100LCDFB [DX3011]
R5F100LCDFC [DX3085]
R5F100LDABG [DX0001]
R5F100LDAFA [DX3012]
R5F100LDAFB [DX3011]
R5F100LDAFC [DX3085]
R5F100LDDBG [DX0001]
R5F100LDDFA [DX3012]
R5F100LDDFB [DX3011]
R5F100LDDFC [DX3085]
R5F100LEABG [DX0001]
R5F100LEAFA [DX3012]
R5F100LEAFB [DX3011]
R5F100LEAFC [DX3085]
R5F100LEDBG [DX0001]
R5F100LEDFA [DX3012]
R5F100LEDFB [DX3011]
R5F100LEDFC [DX3085]
R5F100LFABG [DX0001]
R5F100LFAFA [DX3012]
R5F100LFAFB [DX3011]
R5F100LFAFC [DX3085]
R5F100LFDBG [DX0001]
R5F100LFDFA [DX3012]
R5F100LFDFB [DX3011]
R5F100LFDFC [DX3085]
R5F100LGABG [DX0001]
R5F100LGAFA [DX3012]
R5F100LGAFB [DX3011]
R5F100LGAFC [DX3085]
R5F100LGDBG [DX0001]
R5F100LGDFA [DX3012]
R5F100LGDFB [DX3011]
R5F100LGDFC [DX3085]
R5F100LHABG [DX0001]
R5F100LHAFA [DX3012]
R5F100LHAFB [DX3011]
R5F100LHAFC [DX3085]
R5F100LHDBG [DX0001]
R5F100LHDFA [DX3012]
R5F100LHDFB [DX3011]
R5F100LHDFC [DX3085]
R5F100LJABG [DX0001]
R5F100LJAFA [DX3012]
R5F100LJAFB [DX3011]
R5F100LJAFC [DX3085]
R5F100LJDBG [DX0001]
R5F100LJDFA [DX3012]
R5F100LJDFB [DX3011]
R5F100LJDFC [DX3085]
R5F100LKABG [DX0001]
R5F100LKAFA [DX3012]
R5F100LKAFB [DX3011]
R5F100LKAFC [DX3085]
R5F100LKDBG [DX0001]
R5F100LKDFA [DX3012]
R5F100LKDFB [DX3011]
R5F100LKDFC [DX3085]
R5F100LLABG [DX0001]
R5F100LLAFA [DX3012]
R5F100LLAFB [DX3011]
R5F100LLAFC [DX3085]
R5F100LLDBG [DX0001]
R5F100LLDFA [DX3012]
R5F100LLDFB [DX3011]
R5F100LLDFC [DX3085]
R5F100MCAFA [DX3017]
R5F100MCAFB [DX3016]
R5F100MCDFA [DX3017]
R5F100MCDFB [DX3016]
R5F100MDAFA [DX3017]
R5F100MDAFB [DX3016]
R5F100MDDFA [DX3017]
R5F100MDDFB [DX3016]
R5F100MEAFA [DX3017]
R5F100MEAFB [DX3016]
R5F100MEDFA [DX3017]
R5F100MEDFB [DX3016]
R5F100MFAFA [DX3017]
R5F100MFAFB [DX3016]
R5F100MFDFA [DX3017]
R5F100MFDFB [DX3016]
R5F100MGAFA [DX3017]
R5F100MGAFB [DX3016]

R5F100MGDFA [DX3017]	R5F100MGDFB [DX3016]
R5F100MHAFA [DX3017]	R5F100MHAFB [DX3016]
R5F100MHDFA [DX3017]	R5F100MHDFB [DX3016]
R5F100MJAFA [DX3017]	R5F100MJAFB [DX3016]
R5F100MJDFA [DX3017]	R5F100MJDFB [DX3016]
R5F100MKAFA [DX3017]	R5F100MKAFB [DX3016]
R5F100MKDFA [DX3017]	R5F100MKDFB [DX3016]
R5F100MLAFA [DX3017]	R5F100MLAFB [DX3016]
R5F100MLDFA [DX3017]	R5F100MLDFB [DX3016]
R5F100PCAFA [DX3062]	R5F100PCAFB [DX3021]
R5F100PCDFA [DX3062]	R5F100PCDFB [DX3021]
R5F100PDAFA [DX3062]	R5F100PDAFB [DX3021]
R5F100PDDFA [DX3062]	R5F100PDDFB [DX3021]
R5F100PEAFA [DX3062]	R5F100PEAFB [DX3021]
R5F100PEDFA [DX3062]	R5F100PEDFB [DX3021]
R5F100PFAFA [DX3062]	R5F100PFAFB [DX3021]
R5F100PFDFA [DX3062]	R5F100PFDFB [DX3021]
R5F100PGAFA [DX3062]	R5F100PGAFB [DX3021]
R5F100PGDFA [DX3062]	R5F100PGDFB [DX3021]
R5F100PHAFA [DX3062]	R5F100PHAFB [DX3021]
R5F100PHDFA [DX3062]	R5F100PHDFB [DX3021]
R5F100PJAFA [DX3062]	R5F100PJAFB [DX3021]
R5F100PJDFA [DX3062]	R5F100PJDFB [DX3021]
R5F100PKAFA [DX3062]	R5F100PKAFB [DX3021]
R5F100PKDFA [DX3062]	R5F100PKDFB [DX3021]
R5F100PLAFA [DX3062]	R5F100PLAFB [DX3021]
R5F100PLDFA [DX3062]	R5F100PLDFB [DX3021]
R5F100SCAFB [DX3031]	R5F100SCDFB [DX3031]
R5F100SDAFB [DX3031]	R5F100SDDFB [DX3031]
R5F100SEAFB [DX3031]	R5F100SEDFB [DX3031]
R5F100SFAFB [DX3031]	R5F100SFDFB [DX3031]
R5F100SGAFB [DX3031]	R5F100SGDFB [DX3031]
R5F100SHAFB [DX3031]	R5F100SHDFB [DX3031]
R5F100SJAFB [DX3031]	R5F100SJDFB [DX3031]
R5F100SKAFB [DX3031]	R5F100SKDFB [DX3031]
R5F100SLAFB [DX3031]	R5F100SLDFB [DX3031]
R5F1016AASP [DX1026]	R5F1016ADSP [DX1026]
R5F1016CASP [DX1026]	R5F1016CDSP [DX1026]
R5F1016DASP [DX1026]	R5F1016DDSP [DX1026]
R5F1016EASP [DX1026]	R5F1016EDSP [DX1026]
R5F1016FASP [DX1026]	R5F1016FDSP [DX1026]
R5F1016GASP [DX1026]	R5F1016GDSP [DX1026]
R5F1016HASP [DX1026]	R5F1016HDSP [DX1026]
R5F1016JASP [DX1026]	R5F1016JDSP [DX1026]
R5F1016KASP [DX1026]	R5F1016KDSP [DX1026]
R5F1016LASP [DX1026]	R5F1016LDSP [DX1026]
R5F1017AANA [DX4012]	R5F1017ADNA [DX4012]
R5F1017CANA [DX4012]	R5F1017CDNA [DX4012]

R5F1017DANA [DX4012]
R5F1017DDNA [DX4012]
R5F1017EANA [DX4012]
R5F1017EDNA [DX4012]
R5F1017FANA [DX4012]
R5F1017FDNA [DX4012]
R5F1017GANA [DX4012]
R5F1017GDNA [DX4012]
R5F1017HANA [DX4012]
R5F1017HDNA [DX4012]
R5F1017JANA [DX4012]
R5F1017JDNA [DX4012]
R5F1017KANA [DX4012]
R5F1017KDNA [DX4012]
R5F1017LANA [DX4012]
R5F1017LDNA [DX4012]
R5F1018AALA [DX0001]
R5F1018ADLA [DX0001]
R5F1018CALA [DX0001]
R5F1018CDLA [DX0001]
R5F1018DALA [DX0001]
R5F1018DDLA [DX0001]
R5F1018EALA [DX0001]
R5F1018EDLA [DX0001]
R5F1018FALA [DX0001]
R5F1018FDLA [DX0001]
R5F1018GALA [DX0001]
R5F1018GDLA [DX0001]
R5F1018HALA [DX0001]
R5F1018HDLA [DX0001]
R5F1018JALA [DX0001]
R5F1018JDLA [DX0001]
R5F1018KALA [DX0001]
R5F1018KDLA [DX0001]
R5F1018LALA [DX0001]
R5F1018LDLA [DX0001]
R5F101AAASP [DX1026]
R5F101AADSP [DX1026]
R5F101ACASP [DX1026]
R5F101ACDSP [DX1026]
R5F101ADASP [DX1026]
R5F101ADDSP [DX1026]
R5F101AEASP [DX1026]
R5F101AEDSP [DX1026]
R5F101AFASP [DX1026]
R5F101AFDSP [DX1026]
R5F101AGASP [DX1026]
R5F101AGDSP [DX1026]
R5F101AHASP [DX1026]
R5F101AHDSP [DX1026]
R5F101AJASP [DX1026]
R5F101AJDSP [DX1026]
R5F101AKASP [DX1026]
R5F101AKDSP [DX1026]
R5F101ALASP [DX1026]
R5F101ALDSP [DX1026]
R5F101BAANA [DX4015]
R5F101BADNA [DX4015]
R5F101BCANA [DX4015]
R5F101BCDNA [DX4015]
R5F101BDANA [DX4015]
R5F101BDDNA [DX4015]
R5F101BEANA [DX4015]
R5F101BEDNA [DX4015]
R5F101BFANA [DX4015]
R5F101BFDNA [DX4015]
R5F101BGANA [DX4015]
R5F101BGDNA [DX4015]
R5F101BHANA [DX4015]
R5F101BHDNA [DX4015]
R5F101BJANA [DX4015]
R5F101BJDNA [DX4015]
R5F101BKANA [DX4015]
R5F101BKDNA [DX4015]
R5F101BLANA [DX4015]
R5F101BLDNA [DX4015]
R5F101CAALA [DX0001]
R5F101CADLA [DX0001]
R5F101CCALA [DX0001]
R5F101CCDLA [DX0001]
R5F101CDALA [DX0001]
R5F101CDDLA [DX0001]
R5F101CEALA [DX0001]
R5F101CEDLA [DX0001]
R5F101CFALA [DX0001]
R5F101CFDLA [DX0001]
R5F101CGALA [DX0001]
R5F101CGDLA [DX0001]
R5F101CHALA [DX0001]
R5F101CHDLA [DX0001]
R5F101CJALA [DX0001]
R5F101CJDLA [DX0001]
R5F101CKALA [DX0001]
R5F101CKDLA [DX0001]
R5F101CLALA [DX0001]
R5F101CLDLA [DX0001]

R5F101EAANA [DX4017]	R5F101EADNA [DX4017]
R5F101ECANA [DX4017]	R5F101ECDNA [DX4017]
R5F101EDANA [DX4017]	R5F101EDDNA [DX4017]
R5F101EEANA [DX4017]	R5F101EEDNA [DX4017]
R5F101EFANA [DX4017]	R5F101EFDNA [DX4017]
R5F101EGANA [DX4017]	R5F101EGDNA [DX4017]
R5F101EHANA [DX4017]	R5F101EHDNA [DX4017]
R5F101EJANA [DX4017]	R5F101EJDNA [DX4017]
R5F101EKANA [DX4017]	R5F101EKDNA [DX4017]
R5F101ELANA [DX4017]	R5F101ELDNA [DX4017]
R5F101FAAFP [DX3005]	R5F101FADFP [DX3005]
R5F101FCAFP [DX3005]	R5F101FCDFP [DX3005]
R5F101FDAFP [DX3005]	R5F101FDDFP [DX3005]
R5F101FEAFP [DX3005]	R5F101FEDFP [DX3005]
R5F101FFAFP [DX3005]	R5F101FFDFP [DX3005]
R5F101FGAFP [DX3005]	R5F101FGDFP [DX3005]
R5F101FHAFP [DX3005]	R5F101FHDFP [DX3005]
R5F101FJAFP [DX3005]	R5F101FJDFP [DX3005]
R5F101FKAFP [DX3005]	R5F101FKDFP [DX3005]
R5F101FLAFP [DX3005]	R5F101FLDFP [DX3005]
R5F101GAAFB [DX3007]	R5F101GAANA [DX4021]
R5F101GADFB [DX3007]	R5F101GADNA [DX4021]
R5F101GCAFB [DX3007]	R5F101GCANA [DX4021]
R5F101GCDFB [DX3007]	R5F101GCDNA [DX4021]
R5F101GDAFB [DX3007]	R5F101GDANA [DX4021]
R5F101GDDFB [DX3007]	R5F101GDDNA [DX4021]
R5F101GEAFB [DX3007]	R5F101GEANA [DX4021]
R5F101GEDFB [DX3007]	R5F101GEDNA [DX4021]
R5F101GFAFB [DX3007]	R5F101GFANA [DX4021]
R5F101GFDFB [DX3007]	R5F101GFDNA [DX4021]
R5F101GGAFB [DX3007]	R5F101GGANA [DX4021]
R5F101GGDFB [DX3007]	R5F101GGDNA [DX4021]
R5F101GHAFB [DX3007]	R5F101GHANA [DX4021]
R5F101GHDFB [DX3007]	R5F101GHDNA [DX4021]
R5F101GJAFB [DX3007]	R5F101GJANA [DX4021]
R5F101GJDFB [DX3007]	R5F101GJDNA [DX4021]
R5F101GKAFB [DX3007]	R5F101GKANA [DX4021]
R5F101GKDFB [DX3007]	R5F101GKDNA [DX4021]
R5F101GLAFB [DX3007]	R5F101GLANA [DX4021]
R5F101GLDFB [DX3007]	R5F101GLDNA [DX4021]
R5F101JCAFA [DX3010]	R5F101JCDFA [DX3010]
R5F101JDAFA [DX3010]	R5F101JDDFA [DX3010]
R5F101JEAFA [DX3010]	R5F101JEDFA [DX3010]
R5F101JFAFA [DX3010]	R5F101JFDFA [DX3010]
R5F101JGAFA [DX3010]	R5F101JGDFA [DX3010]
R5F101JHAFA [DX3010]	R5F101JHDFA [DX3010]
R5F101JJAFA [DX3010]	R5F101JJDFA [DX3010]
R5F101JKAFA [DX3010]	R5F101JKDFA [DX3010]

R5F101JLAFA [DX3010]
R5F101JLDFA [DX3010]
R5F101LCABG [DX0001]
R5F101LCAFA [DX3011]
R5F101LCAFB [DX3011]
R5F101LCAFC [DX3011]
R5F101LCDBG [DX0001]
R5F101LCDFA [DX3011]
R5F101LCDFB [DX3011]
R5F101LCDFC [DX3011]
R5F101LDABG [DX0001]
R5F101LDAFA [DX3011]
R5F101LDAFB [DX3011]
R5F101LDAFC [DX3011]
R5F101LDDBG [DX0001]
R5F101LDDFA [DX3011]
R5F101LDDFB [DX3011]
R5F101LDDFC [DX3011]
R5F101LEABG [DX0001]
R5F101LEAFA [DX3011]
R5F101LEAFB [DX3011]
R5F101LEAFC [DX3011]
R5F101LEDBG [DX0001]
R5F101LEDFA [DX3011]
R5F101LEDFB [DX3011]
R5F101LEDFC [DX3011]
R5F101LFABG [DX0001]
R5F101LFAFA [DX3011]
R5F101LFAFB [DX3011]
R5F101LFAFC [DX3011]
R5F101LFDBG [DX0001]
R5F101LFDFA [DX3011]
R5F101LFDFB [DX3011]
R5F101LFDFC [DX3011]
R5F101LGABG [DX0001]
R5F101LGAFA [DX3011]
R5F101LGAFB [DX3011]
R5F101LGAFC [DX3011]
R5F101LGDBG [DX0001]
R5F101LGDFA [DX3011]
R5F101LGDFB [DX3011]
R5F101LGDFC [DX3011]
R5F101LHABG [DX0001]
R5F101LHAFA [DX3011]
R5F101LHAFB [DX3011]
R5F101LHAFC [DX3011]
R5F101LHDBG [DX0001]
R5F101LHDFA [DX3011]
R5F101LHDFB [DX3011]
R5F101LHDFC [DX3011]
R5F101LJABG [DX0001]
R5F101LJAFA [DX3011]
R5F101LJAFB [DX3011]
R5F101LJAFC [DX3011]
R5F101LJDBG [DX0001]
R5F101LJDFA [DX3011]
R5F101LJDFB [DX3011]
R5F101LJDFC [DX3011]
R5F101LKABG [DX0001]
R5F101LKAFA [DX3011]
R5F101LKAFB [DX3011]
R5F101LKAFC [DX3011]
R5F101LKDBG [DX0001]
R5F101LKDFA [DX3011]
R5F101LKDFB [DX3011]
R5F101LKDFC [DX3011]
R5F101LLABG [DX0001]
R5F101LLAFA [DX3011]
R5F101LLAFB [DX3011]
R5F101LLAFC [DX3011]
R5F101LLDBG [DX0001]
R5F101LLDFA [DX3011]
R5F101LLDFB [DX3011]
R5F101LLDFC [DX3011]
R5F101MCAFA [DX3017]
R5F101MCAFB [DX3016]
R5F101MCDFA [DX3017]
R5F101MCDFB [DX3016]
R5F101MDAFA [DX3017]
R5F101MDAFB [DX3016]
R5F101MDDFA [DX3017]
R5F101MDDFB [DX3016]
R5F101MEAFA [DX3017]
R5F101MEAFB [DX3016]
R5F101MEDFA [DX3017]
R5F101MEDFB [DX3016]
R5F101MFAFA [DX3017]
R5F101MFAFB [DX3016]
R5F101MFDFA [DX3017]
R5F101MFDFB [DX3016]
R5F101MGAFA [DX3017]
R5F101MGAFB [DX3016]
R5F101MGDFA [DX3017]
R5F101MGDFB [DX3016]
R5F101MHAFA [DX3017]
R5F101MHAFB [DX3016]

R5F101MHDFA [DX3017]
R5F101MJAFA [DX3017]
R5F101MJDFA [DX3017]
R5F101MKAFA [DX3017]
R5F101MKDFA [DX3017]
R5F101MLAFA [DX3017]
R5F101MLDFA [DX3017]
R5F101PCAFA [DX3062]
R5F101PCDFA [DX3062]
R5F101PDAFA [DX3062]
R5F101PDDFA [DX3062]
R5F101PEAFA [DX3062]
R5F101PEDFA [DX3062]
R5F101PFAFA [DX3062]
R5F101PFDFA [DX3062]
R5F101PGAFA [DX3062]
R5F101PGDFA [DX3062]
R5F101PHAFA [DX3062]
R5F101PHDFA [DX3062]
R5F101PJAFA [DX3062]
R5F101PJDFA [DX3062]
R5F101PKAFA [DX3062]
R5F101PKDFA [DX3062]
R5F101PLAFA [DX3062]
R5F101PLDFA [DX3062]
R5F101SCAFB [DX3031]
R5F101SDAFB [DX3031]
R5F101SEAFB [DX3031]
R5F101SFAFB [DX3031]
R5F101SGAFB [DX3031]
R5F101SHAFB [DX3031]
R5F101SJAFB [DX3031]
R5F101SKAFB [DX3031]
R5F101SLAFB [DX3031]
uPD78F9234MC [DX1027]
R5F101MHDFB [DX3016]
R5F101MJAFB [DX3016]
R5F101MJDFB [DX3016]
R5F101MKAFB [DX3016]
R5F101MKDFB [DX3016]
R5F101MLAFB [DX3016]
R5F101MLDFB [DX3016]
R5F101PCAFB [DX3021]
R5F101PCDFB [DX3021]
R5F101PDAFB [DX3021]
R5F101PDDFB [DX3021]
R5F101PEAFB [DX3021]
R5F101PEDFB [DX3021]
R5F101PFAFB [DX3021]
R5F101PFDFB [DX3021]
R5F101PGAFB [DX3021]
R5F101PGDFB [DX3021]
R5F101PHAFB [DX3021]
R5F101PHDFB [DX3021]
R5F101PJAFB [DX3021]
R5F101PJDFB [DX3021]
R5F101PKAFB [DX3021]
R5F101PKDFB [DX3021]
R5F101PLAFB [DX3021]
R5F101PLDFB [DX3021]
R5F101SCDFB [DX3031]
R5F101SDDFB [DX3031]
R5F101SEDFB [DX3031]
R5F101SFDFB [DX3031]
R5F101SGDFB [DX3031]
R5F101SHDFB [DX3031]
R5F101SJDFB [DX3031]
R5F101SKDFB [DX3031]
R5F101SLDFB [DX3031]
uPD78F9234SD [DX0032]

LG Semicon

DRAM & SRAM

GM76C256CL [DX0001]
GM76C256CL@TSOP28 [DX1001]
GM76C256CLL@SSOP28 [DX1063]
GM76C8128CL [DX0001]
GM76C8128CL@TSOP32 [DX1002]
GM76C8128CLL [DX0001]
GM76C8128CLL@TSOP32 [DX1002]
GM76C256CL@SSOP28 [DX1063]
GM76C256CLL [DX0001]
GM76C256CLL@TSOP28 [DX1001]
GM76C8128CL@SSOP32 [DX1019]
GM76C8128CL@VSOP32 [DX1003]
GM76C8128CLL@SSOP32 [DX1019]
GM76C8128CLL@VSOP32 [DX1003]

GM76C88AL [DX0001]
GM76C88AL@SSOP28
GM76C88AL@TSOP28 [DX1001]
GM76U256CL [DX0001]
GM76U256CL@SSOP28
GM76U256CL@TSOP28 [DX1001]
GM76U256CLL [DX0001]
GM76U256CLL@SSOP28
GM76U256CLL@TSOP28 [DX1001]
GM76U8128CL [DX0001]
GM76U8128CL@SSOP32 [DX1019]
GM76U8128CL@TSOP32 [DX1002]
GM76U8128CL@VSOP32 [DX1003]
GM76U8128CLL [DX0001]
GM76U8128CLL@SSOP32 [DX1019]
GM76U8128CLL@TSOP32 [DX1002]
GM76U8128CLL@VSOP32 [DX1003]
GM76U8128DL [DX0001]
GM76U8128DL@SSOP32 [DX1019]
GM76U8128DL@TSOP32 [DX1002]
GM76U8128DL@VSOP32 [DX1003]
GM76U8128DLL [DX0001]
GM76U8128DLL@SSOP32 [DX1019]
GM76U8128DLL@TSOP32 [DX1002]
GM76U8128DLL@VSOP32 [DX1003]
GM76U8512L [DX0001]
GM76U8512L@SSOP32
GM76U8512L@TSOP32 [DX1002]
GM76U8512L@VSOP32 [DX1003]
GM76U8512LL [DX0001]
GM76U8512LL@SSOP32 [DX1019]
GM76U8512LL@TSOP32 [DX1002]
GM76U8512LL@VSOP32 [DX1003]
GM76V256CL [DX0001]
GM76V256CL@SSOP28
GM76V256CL@TSOP28 [DX1001]
GM76V256CLL [DX0001]
GM76V256CLL@SSOP28
GM76V256CLL@TSOP28 [DX1001]
GM76V8128CL [DX0001]
GM76V8128CL@SSOP32 [DX1019]
GM76V8128CL@TSOP32 [DX1002]
GM76V8128CL@VSOP32 [DX1003]
GM76V8128CLL [DX0001]
GM76V8128CLL@SSOP32 [DX1019]
GM76V8128CLL@TSOP32 [DX1002]
GM76V8128CLL@VSOP32 [DX1003]
GM76V8128DL [DX0001]
GM76V8128DL@SSOP32 [DX1019]
GM76V8128DL@TSOP32 [DX1002]
GM76V8128DL@VSOP32 [DX1003]
GM76V8128DLL [DX0001]
GM76V8128DLL@SSOP32 [DX1019]
GM76V8128DLL@TSOP32 [DX1002]
GM76V8128DLL@VSOP32 [DX1003]
GM76V8512L [DX0001]
GM76V8512L@SSOP32 [DX1019]
GM76V8512L@TSOP32 [DX1002]
GM76V8512L@VSOP32 [DX1003]
GM76V8512LL [DX0001]
GM76V8512LL@SSOP32 [DX1019]
GM76V8512LL@TSOP32 [DX1002]
GM76V8512LL@VSOP32 [DX1003]
GM77C8128A [DX0001]
GM77C8128A@SSOP32 [DX1019]
GM77C8128A@TSOP32 [DX1002]
GM77C8128A@VSOP32 [DX1003]

MICROCONTROLLER

GMS34004TK [DX0001]
GMS34004TM [DX0001]
GMS34004TW [DX0001]
GMS34112TK [DX0001]
GMS34112TK@SOIC20 [DX1033]
GMS34112TK@SSOP20 [DX1026]
GMS34140TK [DX0001]
GMS34140TK@SOIC24 [DX1033]
GMS80C701 [DX0001]
GMS80C701@PLCC44 [DX2044]
GMS80C701@TQFP44 [DX3002]
GMS81004(dip20) [DX0001]
GMS81004(dip24) [DX0001]
GMS81004(dip28) [DX0001]
GMS81004@PLCC44 [DX2044]
GMS81004@SOIC20 [DX1033]
GMS81004@SOIC24 [DX1033]
GMS81004@SOIC28 [DX1033]
GMS81008(dip20) [DX0001]
GMS81008(dip24) [DX0001]

GMS81008(dip28) [DX0001]
GMS81008@PLCC44 [DX2044]
GMS81008@SOIC20 [DX1033]
GMS81008@SOIC24 [DX1033]
GMS81008@SOIC28 [DX1033]
GMS81016(dip20) [DX0001]
GMS81016(dip24) [DX0001]
GMS81016(dip28) [DX0001]
GMS81016@PLCC44 [DX2044]
GMS81016@SOIC20 [DX1033]
GMS81016@SOIC24 [DX1033]
GMS81016@SOIC28 [DX1033]
GMS81024(dip20) [DX0001]
GMS81024(dip24) [DX0001]
GMS81024(dip28) [DX0001]
GMS81024@PLCC44 [DX2044]
GMS81024@SOIC20 [DX1033]
GMS81024@SOIC24 [DX1033]
GMS81024@SOIC28 [DX1033]
GMS81032(dip20) [DX0001]
GMS81032(dip24) [DX0001]
GMS81032(dip28) [DX0001]
GMS81032@PLCC44 [DX2044]
GMS81032@SOIC20 [DX1033]
GMS81032@SOIC24 [DX1033]
GMS81032@SOIC28 [DX1033]
GMS81504AT [DX0032]
GMS81504T [DX0032]
GMS81516 [DX0001]
GMS81516@LQFP64 [DX3011]
GMS81516@MQFP64 [DX3015]
GMS81516@SDIP64 [DX0064]
GMS81516AT [DX0001]
GMS81516AT@LQFP64 [DX3011]
GMS81516AT@MQFP64 [DX3015]
GMS81516AT@SDIP64 [DX0064]
GMS81516BT [DX0001]
GMS81516BT@LQFP64 [DX3011]
GMS81516BT@MQFP64 [DX3015]
GMS81516BT@SDIP64 [DX0064]
GMS81524 [DX0001]
GMS81524@LQFP64 [DX3011]
GMS81524@MQFP64 [DX3015]
GMS81524@SDIP64 [DX0064]
GMS81524AT [DX0001]
GMS81524AT@LQFP64 [DX3011]
GMS81524AT@MQFP64 [DX3015]
GMS81524AT@SDIP64 [DX0064]
GMS81524BT [DX0001]
GMS81524BT@LQFP64 [DX3011]
GMS81524BT@MQFP64 [DX3015]
GMS81524BT@SDIP64 [DX0064]
GMS81604T [DX0001]
GMS81604T@PLCC44 [DX2044]
GMS81604T@SDIP42 [DX0042]
GMS81608T [DX0001]
GMS81608T@PLCC44 [DX2044]
GMS81608T@SDIP42 [DX0042]
GMS81C5016(dip28) [DX0001]
GMS81C5016(dip40) [DX0001]
GMS81C5016@PLCC44 [DX2044]
GMS81C5016@SOIC28 [DX1033]
GMS81C5016@TQFP44 [DX3002]
GMS81C5024(dip28) [DX0001]
GMS81C5024(dip40) [DX0001]
GMS81C5024@PLCC44 [DX2044]
GMS81C5024@SOIC28 [DX1033]
GMS81C5024@TQFP44 [DX3002]
GMS81C5032(dip28) [DX0001]
GMS81C5032(dip40) [DX0001]
GMS81C5032@PLCC44 [DX2044]
GMS81C5032@SOIC28 [DX1033]
GMS81C5032@TQFP44 [DX3002]
GMS82516T [DX0001]
GMS82516T@LQFP64 [DX3011]
GMS82516T@MQFP44 [DX3002]
GMS82516T@MQFP64 [DX3015]
GMS82516T@SDIP42 [DX0042]
GMS82516T@SDIP64 [DX0064]
GMS82524T [DX0001]
GMS82524T@LQFP64 [DX3011]
GMS82524T@MQFP44 [DX3002]
GMS82524T@MQFP64 [DX3015]
GMS82524T@SDIP42 [DX0042]
GMS82524T@SDIP64 [DX0064]
GMS84512T@SDIP52 [DX0056]
GMS84524T@SDIP52 [DX0056]
GMS87C1102 [DX0001]
GMS87C1102@SOP16 [DX1033]
GMS87C1202 [DX0001]
GMS87C1202@SOP20 [DX1033]
GMS87C1404 [DX0001]
GMS87C1404@SOP28 [DX1033]
GMS87C1408 [DX0001]
GMS87C1408@SOP28 [DX1033]
GMS87C2020@LQFP64 [DX3011]

GMS87C2020@MQFP64 [DX3015]
GMS87C2020@SDIP64 [DX0064]
GMS87C5032(dip28) [DX0001]
GMS87C5032(dip40) [DX0001]
GMS87C5032@PLCC44 [DX2044]
GMS87C5032@SOIC28 [DX1033]
GMS87C5032@TQFP44 [DX3002]
GMS87C5108@PQFP80 [DX3019]
GMS87C7008@LQFP64 [DX3011]
GMS87C7008@MQFP64 [DX3015]
GMS87C7008@SDIP64 [DX0064]
GMS87C7016@LQFP64 [DX3011]
GMS87C7016@MQFP64 [DX3015]
GMS87C7016@SDIP64 [DX0064]
GMS97C1051 [DX0001]
GMS97C1051@SOIC20 [DX1033]
GMS97C2051 [DX0001]
GMS97C2051@SOIC20 [DX1033]
GMS97C51 [DX0001]
GMS97C51@PLCC44 [DX2044]
GMS97C51@TQFP44 [DX3002]
GMS97C52 [DX0001]
GMS97C52@PLCC44 [DX2044]
GMS97C52@TQFP44 [DX3002]
GMS97C54 [DX0001]
GMS97C54@PLCC44 [DX2044]
GMS97C54@TQFP44 [DX3002]
GMS97C56 [DX0001]
GMS97C56@PLCC44 [DX2044]
GMS97C56@TQFP44 [DX3002]
GMS97C58 [DX0001]
GMS97C58@PLCC44 [DX2044]
GMS97C58@TQFP44 [DX3002]
GMS97L1051 [DX0001]
GMS97L1051@SOIC20 [DX1033]
GMS97L2051 [DX0001]
GMS97L2051@SOIC20 [DX1033]
GMS97L51 [DX0001]
GMS97L51@PLCC44 [DX2044]
GMS97L51@TQFP44 [DX3002]
GMS97L52 [DX0001]
GMS97L52@PLCC44 [DX2044]
GMS97L52@TQFP44 [DX3002]
GMS97L54 [DX0001]
GMS97L54@PLCC44 [DX2044]
GMS97L54@TQFP44 [DX3002]
GMS97L56 [DX0001]
GMS97L56@PLCC44 [DX2044]
GMS97L56@TQFP44 [DX3002]
GMS97L58 [DX0001]
GMS97L58@PLCC44 [DX2044]
GMS97L58@TQFP44 [DX3002]
GMS99C51 [DX0001]
GMS99C51@PLCC44 [DX2044]
GMS99C51@TQFP44 [DX3002]
GMS99C52 [DX0001]
GMS99C52@PLCC44 [DX2044]
GMS99C52@TQFP44 [DX3002]
GMS99C58 [DX0001]
GMS99C58@PLCC44 [DX2044]
GMS99C58@TQFP44 [DX3002]

LGEPARTNER

MICROCONTROLLER

MN101EF56K [BBBB]
MN101EF57G [DX3017]
MN101EF76K [BBBB]

lierda

MICROCONTROLLER

LSD1M-5001@QFN32 [DX4060-3]
LSD1M-5001@QFN32(left down) [DX4060-4]

LINEAR

MICROCONTROLLER

LTC2978@QFN64 [DX4023]
LTC3880@QFN64 [DX4023]

LINKSMART

E(E)PROM/FRAM/NVRAM

L24C02 [DX0001]
L24C02@SSOP8 [DX1045]
L24C02@TSOP8 [DX1059]
L24C04 [DX0001]
L24C04@SSOP8 [DX1045]
L24C04@TSOP8 [DX1059]
L29004C [DX0001]
L29004C@PLCC32 [DX2032]
L29004C@TSOP32 [DX1002]
L29S160F@TSOP48 [DX1004]
L29S160F-B@TSOP48 [DX1004]
L29S400F@PSOP44 [DX1014]
L29S400F@TSOP48 [DX1004]
L29S400F-B@PSOP44 [DX1014]
L29S400F-B@TSOP48 [DX1004]
L29S800F@TSOP48 [DX1004]
L29S800F-B@TSOP48 [DX1004]
L29W800E@TSOP48 [DX1004]
L29W800E-B@TSOP48 [DX1004]
LST28001 [DX0001]
LST28001@PLCC32 [DX2032]
LST28001@TSOP32 [DX1002]
LST28002 [DX0001]
LST28002@PLCC32 [DX2032]
LST28002@TSOP32 [DX1002]
LST28004 [DX0001]
LST28004@PLCC32 [DX2032]
LST28004@TSOP32 [DX1002]

LITAO

E(E)PROM/FRAM/NVRAM

L24C01 [DX0001]
L24C02 [DX0001]
L24C04 [DX0001]
L24C08 [DX0001]
L24C16 [DX0001]

LIZE

E(E)PROM/FRAM/NVRAM

L24C02 [DX0001]
L24C02@SOP8 [DX1045]
L24C02@TSSOP8 [DX1059]
L24C04 [DX0001]
L24C04@SOP8 [DX1045]
L24C04@TSSOP8 [DX1059]
L24C08 [DX0001]
L24C08@SOP8 [DX1045]
L24C08@TSSOP8 [DX1059]
L24C16 [DX0001]
L24C16@SOP8 [DX1045]
L24C16@TSSOP8 [DX1059]

LUMINARY

MICROCONTROLLER

LM3S101(new)@SOIC28 [DX1033]
LM3S101(new)@SOIC28(ISP) [DX0001]
LM3S101(old)@SOIC28 [DX1033]
LM3S101(old)@SOIC28(ISP) [DX0001]
LM3S102(new)@SOIC28 [DX1033]
LM3S102(new)@SOIC28(ISP) [DX0001]
LM3S102(old)@SOIC28 [DX1033]
LM3S102(old)@SOIC28(ISP) [DX0001]

LM3S1110@BGA108 [DX5107]	LM3S1110@BGA108(ISP) [DX0001]
LM3S1110@TQFP100 [DX3021]	LM3S1110@TQFP100(ISP) [DX0001]
LM3S1133@BGA108 [DX5107]	LM3S1133@BGA108(ISP) [DX0001]
LM3S1133@TQFP100 [DX3021]	LM3S1133@TQFP100(ISP) [DX0001]
LM3S1138@BGA108 [DX5107]	LM3S1138@BGA108(ISP) [DX0001]
LM3S1138@TQFP100 [DX3021]	LM3S1138@TQFP100(ISP) [DX0001]
LM3S1150@BGA108 [DX5107]	LM3S1150@BGA108(ISP) [DX0001]
LM3S1150@TQFP100 [DX3021]	LM3S1150@TQFP100(ISP) [DX0001]
LM3S1162@BGA108 [DX5107]	LM3S1162@BGA108(ISP) [DX0001]
LM3S1162@TQFP100 [DX3021]	LM3S1162@TQFP100(ISP) [DX0001]
LM3S1165@BGA108 [DX5107]	LM3S1165@BGA108(ISP) [DX0001]
LM3S1165@TQFP100 [DX3021]	LM3S1165@TQFP100(ISP) [DX0001]
LM3S1332@BGA108 [DX5107]	LM3S1332@BGA108(ISP) [DX0001]
LM3S1332@TQFP100 [DX3021]	LM3S1332@TQFP100(ISP) [DX0001]
LM3S1435@BGA108 [DX5107]	LM3S1435@BGA108(ISP) [DX0001]
LM3S1435@TQFP100 [DX3021]	LM3S1435@TQFP100(ISP) [DX0001]
LM3S1439@BGA108 [DX5107]	LM3S1439@BGA108(ISP) [DX0001]
LM3S1439@TQFP100 [DX3021]	LM3S1439@TQFP100(ISP) [DX0001]
LM3S1512@BGA108 [DX5107]	LM3S1512@BGA108(ISP) [DX0001]
LM3S1512@TQFP100 [DX3021]	LM3S1512@TQFP100(ISP) [DX0001]
LM3S1538@BGA108 [DX5107]	LM3S1538@BGA108(ISP) [DX0001]
LM3S1538@TQFP100 [DX3021]	LM3S1538@TQFP100(ISP) [DX0001]
LM3S1601@BGA108 [DX5107]	LM3S1601@BGA108(ISP) [DX0001]
LM3S1601@TQFP100 [DX3021]	LM3S1601@TQFP100(ISP) [DX0001]
LM3S1607@TQFP64 [DX3011]	LM3S1607@TQFP64(ISP) [DX0001]
LM3S1608@BGA108 [DX5107]	LM3S1608@BGA108(ISP) [DX0001]
LM3S1608@TQFP100 [DX3021]	LM3S1608@TQFP100(ISP) [DX0001]
LM3S1620@BGA108 [DX5107]	LM3S1620@BGA108(ISP) [DX0001]
LM3S1620@TQFP100 [DX3021]	LM3S1620@TQFP100(ISP) [DX0001]
LM3S1625@TQFP64 [DX3011]	LM3S1625@TQFP64(ISP) [DX0001]
LM3S1626@TQFP64 [DX3011]	LM3S1626@TQFP64(ISP) [DX0001]
LM3S1627@TQFP64 [DX3011]	LM3S1627@TQFP64(ISP) [DX0001]
LM3S1635@BGA108 [DX5107]	LM3S1635@BGA108(ISP) [DX0001]
LM3S1635@TQFP100 [DX3021]	LM3S1635@TQFP100(ISP) [DX0001]
LM3S1637@BGA108 [DX5107]	LM3S1637@BGA108(ISP) [DX0001]
LM3S1637@TQFP100 [DX3021]	LM3S1637@TQFP100(ISP) [DX0001]

LM3S1751@BGA108 [DX5107]	LM3S1751@BGA108(ISP) [DX0001]
LM3S1751@TQFP100 [DX3021]	LM3S1751@TQFP100(ISP) [DX0001]
LM3S1776@TQFP64 [DX3011]	LM3S1776@TQFP64(ISP) [DX0001]
LM3S1850@BGA108 [DX5107]	LM3S1850@BGA108(ISP) [DX0001]
LM3S1850@TQFP100 [DX3021]	LM3S1850@TQFP100(ISP) [DX0001]
LM3S1911@BGA108 [DX5107]	LM3S1911@BGA108(ISP) [DX0001]
LM3S1911@TQFP100 [DX3021]	LM3S1911@TQFP100(ISP) [DX0001]
LM3S1918@BGA108 [DX5107]	LM3S1918@BGA108(ISP) [DX0001]
LM3S1918@TQFP100 [DX3021]	LM3S1918@TQFP100(ISP) [DX0001]
LM3S1937@BGA108 [DX5107]	LM3S1937@BGA108(ISP) [DX0001]
LM3S1937@TQFP100 [DX3021]	LM3S1937@TQFP100(ISP) [DX0001]
LM3S1958@BGA108 [DX5107]	LM3S1958@BGA108(ISP) [DX0001]
LM3S1958@TQFP100 [DX3021]	LM3S1958@TQFP100(ISP) [DX0001]
LM3S1960@BGA108 [DX5107]	LM3S1960@BGA108(ISP) [DX0001]
LM3S1960@TQFP100 [DX3021]	LM3S1960@TQFP100(ISP) [DX0001]
LM3S1968@BGA108 [DX5107]	LM3S1968@BGA108(ISP) [DX0001]
LM3S1968@TQFP100 [DX3021]	LM3S1968@TQFP100(ISP) [DX0001]
LM3S2016@BGA108 [DX5107]	LM3S2016@BGA108(ISP) [DX0001]
LM3S2016@TQFP100 [DX3021]	LM3S2016@TQFP100(ISP) [DX0001]
LM3S2110@BGA108 [DX5107]	LM3S2110@BGA108(ISP) [DX0001]
LM3S2110@TQFP100 [DX3021]	LM3S2110@TQFP100(ISP) [DX0001]
LM3S2139@BGA108 [DX5107]	LM3S2139@BGA108(ISP) [DX0001]
LM3S2139@TQFP100 [DX3021]	LM3S2139@TQFP100(ISP) [DX0001]
LM3S2276@TQFP64 [DX3011]	LM3S2276@TQFP64(ISP) [DX0001]
LM3S2410@BGA108 [DX5107]	LM3S2410@BGA108(ISP) [DX0001]
LM3S2410@TQFP100 [DX3021]	LM3S2410@TQFP100(ISP) [DX0001]
LM3S2412@BGA108 [DX5107]	LM3S2412@BGA108(ISP) [DX0001]
LM3S2412@TQFP100 [DX3021]	LM3S2412@TQFP100(ISP) [DX0001]
LM3S2432@BGA108 [DX5107]	LM3S2432@BGA108(ISP) [DX0001]
LM3S2432@TQFP100 [DX3021]	LM3S2432@TQFP100(ISP) [DX0001]
LM3S2533@BGA108 [DX5107]	LM3S2533@BGA108(ISP) [DX0001]
LM3S2533@TQFP100 [DX3021]	LM3S2533@TQFP100(ISP) [DX0001]
LM3S2601@BGA108 [DX5107]	LM3S2601@BGA108(ISP) [DX0001]
LM3S2601@TQFP100 [DX3021]	LM3S2601@TQFP100(ISP) [DX0001]
LM3S2608@BGA108 [DX5107]	LM3S2608@BGA108(ISP) [DX0001]
LM3S2608@TQFP100 [DX3021]	LM3S2608@TQFP100(ISP) [DX0001]
LM3S2616@TQFP64 [DX3011]	LM3S2616@TQFP64(ISP) [DX0001]
LM3S2620@BGA108 [DX5107]	LM3S2620@BGA108(ISP) [DX0001]
LM3S2620@TQFP100 [DX3021]	LM3S2620@TQFP100(ISP) [DX0001]
LM3S2637@BGA108 [DX5107]	LM3S2637@BGA108(ISP) [DX0001]
LM3S2637@TQFP100 [DX3021]	LM3S2637@TQFP100(ISP) [DX0001]
LM3S2651@BGA108 [DX5107]	LM3S2651@BGA108(ISP) [DX0001]
LM3S2651@TQFP100 [DX3021]	LM3S2651@TQFP100(ISP) [DX0001]
LM3S2671@TQFP64 [DX3011]	LM3S2671@TQFP64(ISP) [DX0001]
LM3S2678@TQFP64 [DX3011]	LM3S2678@TQFP64(ISP) [DX0001]
LM3S2730@BGA108 [DX5107]	LM3S2730@BGA108(ISP) [DX0001]
LM3S2730@TQFP100 [DX3021]	LM3S2730@TQFP100(ISP) [DX0001]
LM3S2739@BGA108 [DX5107]	LM3S2739@BGA108(ISP) [DX0001]

LM3S2739@TQFP100 [DX3021]	LM3S2739@TQFP100(ISP) [DX0001]
LM3S2776@TQFP64 [DX3011]	LM3S2776@TQFP64(ISP) [DX0001]
LM3S2911@BGA108 [DX5107]	LM3S2911@BGA108(ISP) [DX0001]
LM3S2911@TQFP100 [DX3021]	LM3S2911@TQFP100(ISP) [DX0001]
LM3S2918@BGA108 [DX5107]	LM3S2918@BGA108(ISP) [DX0001]
LM3S2918@TQFP100 [DX3021]	LM3S2918@TQFP100(ISP) [DX0001]
LM3S2939@BGA108 [DX5107]	LM3S2939@BGA108(ISP) [DX0001]
LM3S2939@TQFP100 [DX3021]	LM3S2939@TQFP100(ISP) [DX0001]
LM3S2948@BGA108 [DX5107]	LM3S2948@BGA108(ISP) [DX0001]
LM3S2948@TQFP100 [DX3021]	LM3S2948@TQFP100(ISP) [DX0001]
LM3S2950@BGA108 [DX5107]	LM3S2950@BGA108(ISP) [DX0001]
LM3S2950@TQFP100 [DX3021]	LM3S2950@TQFP100(ISP) [DX0001]
LM3S2965@BGA108 [DX5107]	LM3S2965@BGA108(ISP) [DX0001]
LM3S2965@TQFP100 [DX3021]	LM3S2965@TQFP100(ISP) [DX0001]
LM3S300@LQFP48 [DX3007]	LM3S300@LQFP48(ISP) [DX0001]
LM3S301(new)@LQFP48 [DX3007]	
LM3S301(new)@LQFP48(ISP) [DX0001]	
LM3S301(old)@LQFP48 [DX3007]	
LM3S301(old)@LQFP48(ISP) [DX0001]	
LM3S308@LQFP48 [DX3007]	LM3S308@LQFP48(ISP) [DX0001]
LM3S310(new)@LQFP48 [DX3007]	
LM3S310(new)@LQFP48(ISP) [DX0001]	
LM3S310(old)@LQFP48 [DX3007]	
LM3S310(old)@LQFP48(ISP) [DX0001]	
LM3S315(new)@LQFP48 [DX3007]	
LM3S315(new)@LQFP48(ISP) [DX0001]	
LM3S315(old)@LQFP48 [DX3007]	
LM3S315(old)@LQFP48(ISP) [DX0001]	
LM3S316(new)@LQFP48 [DX3007]	
LM3S316(new)@LQFP48(ISP) [DX0001]	
LM3S316(old)@LQFP48 [DX3007]	
LM3S316(old)@LQFP48(ISP) [DX0001]	
LM3S317(new)@LQFP48 [DX3007]	
LM3S317(new)@LQFP48(ISP) [DX0001]	
LM3S317(old)@LQFP48 [DX3007]	
LM3S317(old)@LQFP48(ISP) [DX0001]	
LM3S328(new)@LQFP48 [DX3007]	
LM3S328(new)@LQFP48(ISP) [DX0001]	
LM3S328(old)@LQFP48 [DX3007]	
LM3S328(old)@LQFP48(ISP) [DX0001]	
LM3S3651@TQFP64 [DX3011]	LM3S3651@TQFP64(ISP) [DX0001]
LM3S3739@BGA108 [DX5107]	LM3S3739@BGA108(ISP) [DX0001]
LM3S3739@TQFP100 [DX3021]	LM3S3739@TQFP100(ISP) [DX0001]
LM3S3748@BGA108 [DX5107]	LM3S3748@BGA108(ISP) [DX0001]
LM3S3748@TQFP100 [DX3021]	LM3S3748@TQFP100(ISP) [DX0001]
LM3S3749@BGA108 [DX5107]	LM3S3749@BGA108(ISP) [DX0001]
LM3S3749@TQFP100 [DX3021]	LM3S3749@TQFP100(ISP) [DX0001]
LM3S3759@BGA108 [DX5107]	LM3S3759@BGA108(ISP) [DX0001]

LM3S3759@TQFP100 [DX3021]	LM3S3759@TQFP100(ISP) [DX0001]
LM3S3768@BGA108 [DX5107]	LM3S3768@BGA108(ISP) [DX0001]
LM3S3768@TQFP100 [DX3021]	LM3S3768@TQFP100(ISP) [DX0001]
LM3S5632@TQFP64 [DX3011]	LM3S5632@TQFP64(ISP) [DX0001]
LM3S5652@TQFP64 [DX3011]	LM3S5652@TQFP64(ISP) [DX0001]
LM3S5662@TQFP64 [DX3011]	LM3S5662@TQFP64(ISP) [DX0001]
LM3S5732@TQFP64 [DX3011]	LM3S5732@TQFP64(ISP) [DX0001]
LM3S5737@BGA108 [DX5107]	LM3S5737@BGA108(ISP) [DX0001]
LM3S5737@TQFP100 [DX3021]	LM3S5737@TQFP100(ISP) [DX0001]
LM3S5739@BGA108 [DX5107]	LM3S5739@BGA108(ISP) [DX0001]
LM3S5739@TQFP100 [DX3021]	LM3S5739@TQFP100(ISP) [DX0001]
LM3S5747@BGA108 [DX5107]	LM3S5747@BGA108(ISP) [DX0001]
LM3S5747@TQFP100 [DX3021]	LM3S5747@TQFP100(ISP) [DX0001]
LM3S5749@BGA108 [DX5107]	LM3S5749@BGA108(ISP) [DX0001]
LM3S5749@TQFP100 [DX3021]	LM3S5749@TQFP100(ISP) [DX0001]
LM3S5752@TQFP64 [DX3011]	LM3S5752@TQFP64(ISP) [DX0001]
LM3S5757@BGA108 [DX5107]	LM3S5757@BGA108(ISP) [DX0001]
LM3S5757@TQFP100 [DX3021]	LM3S5757@TQFP100(ISP) [DX0001]
LM3S5762@TQFP64 [DX3011]	LM3S5762@TQFP64(ISP) [DX0001]
LM3S5767@BGA108 [DX5107]	LM3S5767@BGA108(ISP) [DX0001]
LM3S5767@TQFP100 [DX3021]	LM3S5767@TQFP100(ISP) [DX0001]
LM3S5768@BGA108 [DX5107]	LM3S5768@BGA108(ISP) [DX0001]
LM3S5768@TQFP100 [DX3021]	LM3S5768@TQFP100(ISP) [DX0001]
LM3S5769@BGA108 [DX5107]	LM3S5769@BGA108(ISP) [DX0001]
LM3S5769@TQFP100 [DX3021]	LM3S5769@TQFP100(ISP) [DX0001]
LM3S600@LQFP48 [DX3007]	LM3S600@LQFP48(ISP) [DX0001]
LM3S601(new)@LQFP48 [DX3007]	
LM3S601(new)@LQFP48(ISP) [DX0001]	
LM3S601(old)@LQFP48 [DX3007]	
LM3S601(old)@LQFP48(ISP) [DX0001]	
LM3S608@LQFP48 [DX3007]	LM3S608@LQFP48(ISP) [DX0001]
LM3S610(new)@LQFP48 [DX3007]	
LM3S610(new)@LQFP48(ISP) [DX0001]	
LM3S610(old)@LQFP48 [DX3007]	
LM3S610(old)@LQFP48(ISP) [DX0001]	
LM3S6100@BGA108 [DX5107]	LM3S6100@BGA108(ISP) [DX0001]
LM3S6100@TQFP100 [DX3021]	LM3S6100@TQFP100(ISP) [DX0001]
LM3S611(new)@LQFP48 [DX3007]	
LM3S611(new)@LQFP48(ISP) [DX0001]	
LM3S611(old)@LQFP48 [DX3007]	
LM3S611(old)@LQFP48(ISP) [DX0001]	
LM3S6110@BGA108 [DX5107]	LM3S6110@BGA108(ISP) [DX0001]
LM3S6110@TQFP100 [DX3021]	LM3S6110@TQFP100(ISP) [DX0001]
LM3S612(new)@LQFP48 [DX3007]	
LM3S612(new)@LQFP48(ISP) [DX0001]	
LM3S612(old)@LQFP48 [DX3007]	
LM3S612(old)@LQFP48(ISP) [DX0001]	
LM3S613(new)@LQFP48 [DX3007]	

LM3S613(new)@LQFP48(ISP) [DX0001]
LM3S613(old)@LQFP48 [DX3007]
LM3S613(old)@LQFP48(ISP) [DX0001]
LM3S615(new)@LQFP48 [DX3007]
LM3S615(new)@LQFP48(ISP) [DX0001]
LM3S615(old)@LQFP48 [DX3007]
LM3S615(old)@LQFP48(ISP) [DX0001]
LM3S617(new)@LQFP48 [DX3007]
LM3S617(new)@LQFP48(ISP) [DX0001]
LM3S617(old)@LQFP48 [DX3007]
LM3S617(old)@LQFP48(ISP) [DX0001]
LM3S618(new)@LQFP48 [DX3007]
LM3S618(new)@LQFP48(ISP) [DX0001]
LM3S618(old)@LQFP48 [DX3007]
LM3S618(old)@LQFP48(ISP) [DX0001]
LM3S628(new)@LQFP48 [DX3007]
LM3S628(new)@LQFP48(ISP) [DX0001]
LM3S628(old)@LQFP48 [DX3007]
LM3S628(old)@LQFP48(ISP) [DX0001]
LM3S6420@BGA108 [DX5107]
LM3S6420@BGA108(ISP) [DX0001]
LM3S6420@TQFP100 [DX3021]
LM3S6420@TQFP100(ISP) [DX0001]
LM3S6422@BGA108 [DX5107]
LM3S6422@BGA108(ISP) [DX0001]
LM3S6422@TQFP100 [DX3021]
LM3S6422@TQFP100(ISP) [DX0001]
LM3S6432@BGA108 [DX5107]
LM3S6432@BGA108(ISP) [DX0001]
LM3S6432@TQFP100 [DX3021]
LM3S6432@TQFP100(ISP) [DX0001]
LM3S6537@BGA108 [DX5107]
LM3S6537@BGA108(ISP) [DX0001]
LM3S6537@TQFP100 [DX3021]
LM3S6537@TQFP100(ISP) [DX0001]
LM3S6610@BGA108 [DX5107]
LM3S6610@BGA108(ISP) [DX0001]
LM3S6610@TQFP100 [DX3021]
LM3S6610@TQFP100(ISP) [DX0001]
LM3S6611@BGA108 [DX5107]
LM3S6611@BGA108(ISP) [DX0001]
LM3S6611@TQFP100 [DX3021]
LM3S6611@TQFP100(ISP) [DX0001]
LM3S6618@BGA108 [DX5107]
LM3S6618@BGA108(ISP) [DX0001]
LM3S6618@TQFP100 [DX3021]
LM3S6618@TQFP100(ISP) [DX0001]
LM3S6633@BGA108 [DX5107]
LM3S6633@BGA108(ISP) [DX0001]
LM3S6633@TQFP100 [DX3021]
LM3S6633@TQFP100(ISP) [DX0001]
LM3S6637@BGA108 [DX5107]
LM3S6637@BGA108(ISP) [DX0001]
LM3S6637@TQFP100 [DX3021]
LM3S6637@TQFP100(ISP) [DX0001]
LM3S6730@BGA108 [DX5107]
LM3S6730@BGA108(ISP) [DX0001]
LM3S6730@TQFP100 [DX3021]
LM3S6730@TQFP100(ISP) [DX0001]
LM3S6753@BGA108 [DX5107]
LM3S6753@BGA108(ISP) [DX0001]
LM3S6753@TQFP100 [DX3021]
LM3S6753@TQFP100(ISP) [DX0001]
LM3S6816@BGA108 [DX5107]
LM3S6816@BGA108(ISP) [DX0001]
LM3S6816@TQFP100 [DX3021]
LM3S6816@TQFP100(ISP) [DX0001]
LM3S6911@BGA108 [DX5107]
LM3S6911@BGA108(ISP) [DX0001]
LM3S6911@TQFP100 [DX3021]
LM3S6911@TQFP100(ISP) [DX0001]
LM3S6916@BGA108 [DX5107]
LM3S6916@BGA108(ISP) [DX0001]
LM3S6916@TQFP100 [DX3021]
LM3S6916@TQFP100(ISP) [DX0001]
LM3S6918@BGA108 [DX5107]
LM3S6918@BGA108(ISP) [DX0001]

LM3S6918@TQFP100 [DX3021]	LM3S6918@TQFP100(ISP) [DX0001]
LM3S6938@BGA108 [DX5107]	LM3S6938@BGA108(ISP) [DX0001]
LM3S6938@TQFP100 [DX3021]	LM3S6938@TQFP100(ISP) [DX0001]
LM3S6950@BGA108 [DX5107]	LM3S6950@BGA108(ISP) [DX0001]
LM3S6950@TQFP100 [DX3021]	LM3S6950@TQFP100(ISP) [DX0001]
LM3S6952@BGA108 [DX5107]	LM3S6952@BGA108(ISP) [DX0001]
LM3S6952@TQFP100 [DX3021]	LM3S6952@TQFP100(ISP) [DX0001]
LM3S6965@BGA108 [DX5107]	LM3S6965@BGA108(ISP) [DX0001]
LM3S6965@TQFP100 [DX3021]	LM3S6965@TQFP100(ISP) [DX0001]
LM3S800@LQFP48 [DX3007]	LM3S800@LQFP48(ISP) [DX0001]
LM3S801(new)@LQFP48 [DX3007]	
LM3S801(new)@LQFP48(ISP) [DX0001]	
LM3S801(old)@LQFP48 [DX3007]	
LM3S801(old)@LQFP48(ISP) [DX0001]	
LM3S808@LQFP48 [DX3007]	LM3S808@LQFP48(ISP) [DX0001]
LM3S811(new)@LQFP48 [DX3007]	
LM3S811(new)@LQFP48(ISP) [DX0001]	
LM3S811(old)@LQFP48 [DX3007]	
LM3S811(old)@LQFP48(ISP) [DX0001]	
LM3S812(new)@LQFP48 [DX3007]	
LM3S812(new)@LQFP48(ISP) [DX0001]	
LM3S812(old)@LQFP48 [DX3007]	
LM3S812(old)@LQFP48(ISP) [DX0001]	
LM3S815(new)@LQFP48 [DX3007]	
LM3S815(new)@LQFP48(ISP) [DX0001]	
LM3S815(old)@LQFP48 [DX3007]	
LM3S815(old)@LQFP48(ISP) [DX0001]	
LM3S817(new)@LQFP48 [DX3007]	
LM3S817(new)@LQFP48(ISP) [DX0001]	
LM3S817(old)@LQFP48 [DX3007]	
LM3S817(old)@LQFP48(ISP) [DX0001]	
LM3S818(new)@LQFP48 [DX3007]	
LM3S818(new)@LQFP48(ISP) [DX0001]	
LM3S818(old)@LQFP48 [DX3007]	
LM3S818(old)@LQFP48(ISP) [DX0001]	
LM3S828(new)@LQFP48 [DX3007]	
LM3S828(new)@LQFP48(ISP) [DX0001]	
LM3S828(old)@LQFP48 [DX3007]	
LM3S828(old)@LQFP48(ISP) [DX0001]	
LM3S8530@BGA108 [DX5107]	LM3S8530@BGA108(ISP) [DX0001]
LM3S8530@TQFP100 [DX3021]	LM3S8530@TQFP100(ISP) [DX0001]
LM3S8538@BGA108 [DX5107]	LM3S8538@BGA108(ISP) [DX0001]
LM3S8538@TQFP100 [DX3021]	LM3S8538@TQFP100(ISP) [DX0001]
LM3S8630@BGA108 [DX5107]	LM3S8630@BGA108(ISP) [DX0001]
LM3S8630@TQFP100 [DX3021]	LM3S8630@TQFP100(ISP) [DX0001]
LM3S8730@BGA108 [DX5107]	LM3S8730@BGA108(ISP) [DX0001]
LM3S8730@TQFP100 [DX3021]	LM3S8730@TQFP100(ISP) [DX0001]
LM3S8733@BGA108 [DX5107]	LM3S8733@BGA108(ISP) [DX0001]

LM3S8733@TQFP100 [DX3021]
LM3S8733@TQFP100(ISP) [DX0001]
LM3S8738@BGA108 [DX5107]
LM3S8738@BGA108(ISP) [DX0001]
LM3S8738@TQFP100 [DX3021]
LM3S8738@TQFP100(ISP) [DX0001]
LM3S8930@BGA108 [DX5107]
LM3S8930@BGA108(ISP) [DX0001]
LM3S8930@TQFP100 [DX3021]
LM3S8930@TQFP100(ISP) [DX0001]
LM3S8933@BGA108 [DX5107]
LM3S8933@BGA108(ISP) [DX0001]
LM3S8933@TQFP100 [DX3021]
LM3S8933@TQFP100(ISP) [DX0001]
LM3S8938@BGA108 [DX5107]
LM3S8938@BGA108(ISP) [DX0001]
LM3S8938@TQFP100 [DX3021]
LM3S8938@TQFP100(ISP) [DX0001]
LM3S8962@BGA108 [DX5107]
LM3S8962@BGA108(ISP) [DX0001]
LM3S8962@TQFP100 [DX3021]
LM3S8962@TQFP100(ISP) [DX0001]
LM3S8970@BGA108 [DX5107]
LM3S8970@BGA108(ISP) [DX0001]
LM3S8970@TQFP100 [DX3021]
LM3S8970@TQFP100(ISP) [DX0001]
LM3S8971@BGA108 [DX5107]
LM3S8971@BGA108(ISP) [DX0001]
LM3S8971@TQFP100 [DX3021]
LM3S8971@TQFP100(ISP) [DX0001]

LYONTEK

E(E)PROM/FRAM/NVRAM

LY24C02 [DX0001]
LY24C02@SOIC8 [DX1045]
LY24C02@TSSOP8 [DX1059]
LY24C04 [DX0001]
LY24C04@SOIC8 [DX1045]
LY24C04@TSSOP8 [DX1059]
LY24C08 [DX0001]
LY24C08@SOIC8 [DX1045]
LY24C08@TSSOP8 [DX1059]
LY24C16 [DX0001]
LY24C16@SOIC8 [DX1045]
LY24C16@TSSOP8 [DX1059]

MACRONIX

E(E)PROM/FRAM/NVRAM

KH25L1005 [DX0001]
KH25L1005(ISP) [DX0001]
KH25L1005@SON8 [DX4005]
KH25L1005@SON8(ISP) [DX0001]
KH25L1005@SOP8 [DX1045]
KH25L1005@SOP8(ISP) [DX0001]
KH25L1005A [DX0001]
KH25L1005A@SON8 [DX4005#1]
KH25L1005A@SOP8 [DX1045#1]
KH25L12801F@SOP16 [DX1033#1]
KH25L12805D@SON8(Fast Mode) [DX4006#1]
KH25L12805D@SOP16(Fast Mode) [DX1033#1]
KH25L12805N@SOP16 [DX1033#1]
KH25L12805N@SOP16(Fast Mode) [DX1033#1]
KH25L12835F@SOP16 [DX1033#1]
KH25L12835F@SOP8 [DX1044#1]
KH25L12835F@WSON8(6*5mm) [DX4005#1]
KH25L12835F@WSON8(8*6mm) [DX4006#1]
KH25L12855F@TFBGA24(4*6) [DX5157]
KH25L12855F@TFBGA24(5*5) [DX5146]
KH25L1605@SON8 [DX4006#1]

KH25L1605@SON8(Fast Mode) [DX4006#1]
KH25L1605@SOP16 [DX1033#1]
KH25L1605@SOP16(Fast Mode) [DX1033#1]
KH25L1605A@SON8 [DX4006#1]
KH25L1605A@SON8(Fast Mode) [DX4006#1]
KH25L1605A@SOP16 [DX1033#1]
KH25L1605A@SOP16(Fast Mode) [DX1033#1]
KH25L1605A@SOP8 [DX1044#1]
KH25L1605A@SOP8(Fast Mode) [DX1044#1]
KH25L1605D@SON8 [DX4006#1]
KH25L1605D@SON8(Fast Mode) [DX4006#1]
KH25L1605D@SOP16 [DX1033#1]
KH25L1605D@SOP16(Fast Mode) [DX1033#1]
KH25L1605D@SOP8(150)(Fast Mode) [DX1045#1]
KH25L1605D@SOP8(200)(Fast Mode) [DX1044#1]
KH25L1606E [DX0001]
KH25L1606E(512bit) [DX0001]
KH25L1606E(512bit)@SOIC16 [DX1033]
KH25L1606E(512bit)@SOIC8(150mil) [DX1045#1]
KH25L1606E(512bit)@SOIC8(200mil) [DX1044#1]
KH25L1606E(512bit)@USON8 [DX4004#1]
KH25L1606E(512bit)@WSON8 [DX4005#1]
KH25L1606E@SOP16 [DX1033]
KH25L1606E@SOP8(150 mil) [DX1045#1]
KH25L1606E@SOP8(200 mil) [DX1044#1]
KH25L1606E@USON8 [DX4004#1]
KH25L1606E@WSON8 [DX4005#1]
KH25L1636D@SOP16 [DX1033#1]
KH25L1636D@SOP8(150mil) [DX1045#1]
KH25L1636D@SOP8(200mil) [DX1044#1]
KH25L1636D@WSON8 [DX4005#1]
KH25L1673E@SOP8 [DX1044#1]
KH25L2005 [DX0001]
KH25L2005(ISP) [DX0001]
KH25L2005@SON8 [DX4005]
KH25L2005@SON8(ISP) [DX0001]
KH25L2005@SOP8 [DX1045]
KH25L2005@SOP8(ISP) [DX0001]
KH25L2025 [DX0001]
KH25L2025@SON8 [DX4005#1]
KH25L2025@SOP8 [DX1045#1]
KH25L25635F@SOP16 [DX1072#1]
KH25L25635F@WSON8 [DX4006#1]
KH25L3205@SOP16 [DX1033#1]
KH25L3205@SOP16(Fast Mode) [DX1033#1]
KH25L3205@SOP8 [DX1044#1]
KH25L3205@SOP8(Fast Mode) [DX1044#1]
KH25L3205A@SON8 [DX4006#1]
KH25L3205A@SON8(Fast Mode) [DX4006#1]
KH25L3205A@SOP16 [DX1033#1]
KH25L3205A@SOP16(Fast Mode) [DX1033#1]
KH25L3205A@SOP8 [DX1044#1]
KH25L3205A@SOP8(Fast Mode) [DX1044#1]
KH25L3205D@SON8(Fast Mode) [DX4006#1]
KH25L3205D@SOP16 [DX1033#1]
KH25L3205D@SOP16(Fast Mode) [DX1033#1]
KH25L3205D@SOP8 [DX1044#1]

KH25L3205D@SOP8(Fast Mode) [DX1044#1]
KH25L3206E [DX1044#1]
KH25L3206E(512bit) [DX0001]
KH25L3206E(512bit)@SOIC16 [DX1033#1]
KH25L3206E(512bit)@SOIC8 [DX1044#1]
KH25L3206E(512bit)@USON8 [DX4004#1]
KH25L3206E(512bit)@WSON8 [DX4005#1]
KH25L3206E@SOP16 [DX1033#1]
KH25L3206E@SOP8 [DX1044#1]
KH25L3206E@USON8 [DX4004#1]
KH25L3206E@WSON8 [DX4005#1]
KH25L3236D@SOP16 [DX1033#1]
KH25L3236D@SOP8(150mil) [DX1045#1]
KH25L3236D@SOP8(200mil) [DX1044#1]
KH25L3236D@WSON8 [DX4005#1]
KH25L3239E@SOP8 [DX1044#1]
KH25L3239E@VSOP8 [DX1044#1]
KH25L3239E@WSON8 [DX4005#1]
KH25L3273E@SOP16 [DX1033#1]
KH25L3273E@SOP8 [DX1044#1]
KH25L3273E@VSOP8 [DX1044#1]
KH25L3273E@WSON8 [DX4005#1]
KH25L4005 [DX0001]
KH25L4005(150mil)@SOP8 [DX1045]
KH25L4005(150mil)@SOP8(ISP) [DX0001]
KH25L4005(209mil)@SOP8 [DX1044]
KH25L4005(209mil)@SOP8(ISP) [DX0001]
KH25L4005(ISP) [DX0001]
KH25L4005@SON8 [DX4005]
KH25L4005@SON8(ISP) [DX0001]
KH25L4005A [DX0001]
KH25L4005A(150mil)@SOP8 [DX1045]
KH25L4005A(150mil)@SOP8(ISP) [DX0001]
KH25L4005A(209mil)@SOP8 [DX1044]
KH25L4005A(209mil)@SOP8(ISP) [DX0001]
KH25L4005A(ISP) [DX0001]
KH25L4005A@SON8 [DX4005]
KH25L4005A@SON8(ISP) [DX0001]
KH25L4006E [DX0001]
KH25L4006E@SOP8(150 mil) [DX1045#1]
KH25L4006E@SOP8(200 mil) [DX1044#1]
KH25L4006E@WSON8 [DX4005#1]
KH25L4025A [DX0001]
KH25L4025A(150mil)@SOP8 [DX1045#1]
KH25L4025A(209mil)@SOP8 [DX1044#1]
KH25L4025A@SON8 [DX4005#1]
KH25L512@SON8 [DX4005#1]
KH25L512@SOP8 [DX1045#1]
KH25L5121E@SOP8 [DX1045#1]
KH25L5121E@TSSOP8 [DX1059#1]
KH25L512A [DX0001]
KH25L512A@SON8 [DX4005#1]
KH25L512A@SOP8 [DX1045#1]
KH25L6405@SOP16 [DX1033#1]
KH25L6405@SOP16(Fast Mode) [DX1033#1]
KH25L6405@SOP8 [DX1044#1]
KH25L6405@SOP8(Fast Mode) [DX1044#1]
KH25L6405D@SON8(Fast Mode) [DX4006#1]
KH25L6405D@SOP16 [DX1033#1]
KH25L6405D@SOP16(Fast Mode) [DX1033#1]
KH25L6405D@SOP8 [DX1044#1]
KH25L6405MC@SOP16 [DX1033#1]
KH25L6405MC@SOP8 [DX1044#1]
KH25L6406E@SOP16 [DX1072#1]
KH25L6406E@SOP8 [DX1044#1]
KH25L6406E@WSON8 [DX4006#1]
KH25L6455E@SOP16 [DX1033#1]
KH25L6455E@SOP8 [DX1044#1]
KH25L6455E@TFBGA24 [DX5146]
KH25L6455F@SOP8 [DX1044#1]

KH25L6455F@TFBGA24(4*6) [DX5146]
KH25L6455F@TFBGA24(5*5) [DX5157]
KH25L6473E@SOP16 [DX1033#1]
KH25L6473E@SOP8 [DX1044#1]
KH25L6473E@VSOP8 [DX1044#1]
KH25L6473E@WSON8 [DX4005#1]
KH25L8005 [DX0001]
KH25L8005(150mil)@SOP8 [DX1045#1]
KH25L8005(150mil)@SOP8(ISP) [DX0001]
KH25L8005(209mil)@SOP8 [DX1044#1]
KH25L8005(209mil)@SOP8(ISP) [DX0001]
KH25L8005(ISP) [DX0001]
KH25L8005@SON8 [DX4005#1]
KH25L8005@SON8(ISP) [DX0001]
KH25L8006E [DX0001]
KH25L8006E(512bit) [DX0001]
KH25L8006E(512bit)@SOIC8(150mil) [DX1045#1]
KH25L8006E(512bit)@SOIC8(200mil) [DX1044#1]
KH25L8006E(512bit)@USON8 [DX4004#1]
KH25L8006E(512bit)@WSON8 [DX4005#1]
KH25L8006E@SOP8(150 mil) [DX1045#1]
KH25L8006E@SOP8(200 mil) [DX1044#1]
KH25L8006E@USON8 [DX4004#1]
KH25L8006E@WSON8 [DX4005#1]
KH25L8025 [DX0001]
KH25L8025(150mil)@SOP8 [DX1045#1]
KH25L8025(209mil)@SOP8 [DX1044#1]
KH25L8025@SON8 [DX4005#1]
KH25L8036D [DX0001]
KH25L8036D@SOP16 [DX1033]
KH25L8036D@SOP8(150mil) [DX1045]
KH25L8036D@SOP8(200mil) [DX1044]
KH25L8036D@WSON8 [DX4005]
KH25L8073E@SOP8 [DX1044#1]
KH25U4033E@SOP8 [DX1045#1]
KH25U4033E@TSSOP8 [DX1059#1]
KH25U4033E@USON8 [DX4004#1]
KH25U4033E@WSON8 [DX4005#1]
KH25U6439F@SOP8 [DX1044#1]
KH25U6439F@VSOP8 [DX1044#1]
KH25U6439F@WSON8 [DX4005#1]
KH29GL128FHT2@TSOP56 [DX1011]
KH29GL128FHXF@FBGA64 [DX5074]
KH29GL128FLT2@TSOP56 [DX1011]
KH29GL128FLXF@FBGA64 [DX5074]
KH29GL256FHT2@TSOP56 [DX1011]
KH29GL256FHXF@FBGA64 [DX5074]
KH29GL256FLT2@TSOP56 [DX1011]
KH29GL256FLXF@FBGA64 [DX5074]
KH29GL512FHT2@TSOP56 [DX1011]
KH29GL512FHXF@FBGA64 [DX5074]
KH29GL512FLT2@TSOP56 [DX1011]
KH29GL512FLXF@FBGA64 [DX5074]
KH29GL640EB@TSOP48 [DX1004]
KH29GL640ET@TSOP48 [DX1004]
KH29LV004CB@PLCC32 [DX2032]
KH29LV004CB@TSOP40 [DX1006]
KH29LV004CT@PLCC32 [DX2032]
KH29LV004CT@TSOP40 [DX1006]
KH29LV008CB@TSOP40 [DX1006]
KH29LV008CT@TSOP40 [DX1006]
KH29LV040C [DX0001]
KH29LV040C@PLCC32 [DX2032]
KH29LV160CBT@TSOP48 [DX1004]
KH29LV160CTT@TSOP48 [DX1004]
KH29LV160DBT@TSOP48 [DX1004]
KH29LV160DTT@TSOP48 [DX1004]
KH29LV320CBT@TSOP48 [DX1004]
KH29LV320CTT@TSOP48 [DX1004]
KH29LV320DBT@TSOP48 [DX1004]
KH29LV320DTT@TSOP48 [DX1004]
KH29LV320EBT@TSOP48 [DX1004]
KH29LV320ETT@TSOP48 [DX1004]
KH29LV400CBT@TSOP48 [DX1004]
KH29LV400CTT@TSOP48 [DX1004]
KH29LV640DBT@TSOP48 [DX1004]
KH29LV640DTT@TSOP48 [DX1004]
KH29LV800CBT@TSOP48 [DX1004]
KH29LV800CTT@TSOP48 [DX1004]
KH29SV400CBT@TSOP48 [DX1004]
KH29SV400CTT@TSOP48 [DX1004]

KH68GL1G0FHT2@TSOP56 [DX1011]
KH68GL1G0FHXF@FBGA64 [DX5074]
KH68GL1G0FLT2@TSOP56 [DX1011]
KH68GL1G0FLXF@FBGA64 [DX5074]
MX25L1005 [DX0001]
MX25L1005(ISP) [DX0001]
MX25L1005@SON8 [DX4005]
MX25L1005@SON8(ISP) [DX0001]
MX25L1005@SOP8 [DX1045]
MX25L1005@SOP8(ISP) [DX0001]
MX25L1005@USON8 [DX4002]
MX25L1005A [DX0001]
MX25L1005A@SON8 [DX4005#1]
MX25L1005A@SOP8 [DX1045#1]
MX25L1005C@SOP8 [DX1045]
MX25L1005C@USON8 [DX4002]
MX25L1006E@SOP8 [DX1045#1]
MX25L1006E@USON8 [DX4002#1]
MX25L1006E@WLCSP8 [DX5227#1]
MX25L1021E@SOP8 [DX1045#1]
MX25L1025C@SOP8 [DX1045#1]
MX25L1026E@SOP8 [DX1045#1]
MX25L12801F@SOP16 [DX1033#1]
MX25L12801F@SOP16(Fast Mode) [DX1033#1]
MX25L12805D@SON8(Fast Mode) [DX4006#1]
MX25L12805D@SOP16(512bit OTP) [DX1072#1]
MX25L12805D@SOP16(Fast Mode) [DX1033#1]
MX25L12805D@WSON8(512bit OTP) [DX4006#1]
MX25L12805N@SOP16 [DX1033#1]
MX25L12805N@SOP16(Fast Mode) [DX1033#1]
MX25L12835E@SOP16 [DX1033#1]
MX25L12835E@WSON8 [DX4006#1]
MX25L12835F@SOP16 [DX1033#1]
MX25L12835F@SOP8 [DX1044#1]
MX25L12835F@WSON8(6*5mm) [DX4005#1]
MX25L12835F@WSON8(8*6mm) [DX4006#1]
MX25L12836E@SOP16 [DX1033#1]
MX25L12836E@SOP8 [DX1044#1]
MX25L12836E@WSON8 [DX4006#1]
MX25L12845E@SOP16 [DX1072#1]
MX25L12845E@WSON8 [DX4006#1]
MX25L12845E@WSON8(*) [DX4006#1]
MX25L12845G@SOP16 [DX1033#1]
MX25L12845G@SOP8 [DX1044#1]
MX25L12845G@WSON8 [DX4006#1]
MX25L12855E@SOP16 [DX1033#1]
MX25L12855E@TFBGA24 [DX5146]
MX25L12855F@TFBGA24(4*6) [DX5157]
MX25L12855F@TFBGA24(5*5) [DX5146]
MX25L12865E@SOP16 [DX1033#1]
MX25L12865E@SOP8 [DX1044#1]
MX25L12865E@WSON8 [DX4006#1]
MX25L12865F@SOP16 [DX1033#1]
MX25L12865F@SOP8 [DX1044#1]
MX25L12865F@WSON8 [DX4006#1]
MX25L12873F@SOP16 [DX1033#1]
MX25L12873F@SOP8 [DX1044#1]
MX25L12873F@WSON8 [DX4005#1]
MX25L12875E@SOP16 [DX1033#1]
MX25L12875E@SOP8 [DX1044#1]
MX25L12875E@WSON8 [DX4006#1]
MX25L1605@SON8 [DX4006#1]
MX25L1605@SON8(Fast Mode) [DX4006#1]
MX25L1605@SOP16 [DX1033#1]
MX25L1605@SOP16(Fast Mode) [DX1033#1]
MX25L1605A@SON8 [DX4006#1]
MX25L1605A@SON8(Fast Mode) [DX4006#1]
MX25L1605A@SOP16 [DX1033#1]
MX25L1605A@SOP16(Fast Mode) [DX1033#1]
MX25L1605A@SOP8 [DX1044#1]
MX25L1605A@SOP8(Fast Mode) [DX1044#1]
MX25L1605D(512bit OTP) [DX0001]
MX25L1605D@SON8 [DX4006#1]

MX25L1605D@SON8(Fast Mode) [DX4006#1]
MX25L1605D@SOP16 [DX1033#1]
MX25L1605D@SOP16(512bit OTP) [DX1072#1]
MX25L1605D@SOP16(Fast Mode) [DX1033#1]
MX25L1605D@SOP8(150)(Fast Mode) [DX1045#1]
MX25L1605D@SOP8(200)(Fast Mode) [DX1044#1]
MX25L1605D@SOP8(512bit OTP)(150) [DX1045#1]
MX25L1605D@SOP8(512bit OTP)(200) [DX1044#1]
MX25L1605D@USON8 [DX4004#1]
MX25L1605D@USON8(512bit OTP) [DX4004#1]
MX25L1605D@USON8(Fast Mode) [DX4004#1]
MX25L1605D@WSON8(512bit OTP) [DX4005#1]
MX25L1606E [DX0001]
MX25L1606E(512bit) [DX0001]
MX25L1606E(512bit)@SOIC16 [DX1033]
MX25L1606E(512bit)@SOIC8(150mil) [DX1045#1]
MX25L1606E(512bit)@SOIC8(200mil) [DX1044#1]
MX25L1606E(512bit)@USON8 [DX4004#1]
MX25L1606E(512bit)@WSON8 [DX4005#1]
MX25L1606E@SOP16 [DX1033]
MX25L1606E@SOP8(150 mil) [DX1045#1]
MX25L1606E@SOP8(200 mil) [DX1044#1]
MX25L1606E@USON8 [DX4004#1]
MX25L1606E@WSON8 [DX4005#1]
MX25L1606EG@SOP8(200 mil) [DX1044#1]
MX25L1608D [DX0001]
MX25L1608D@SOP16 [DX1072#1]
MX25L1608D@SOP8(150mil) [DX1045#1]
MX25L1608D@SOP8(200mil) [DX1044#1]
MX25L1608D@USON8 [DX4004#1]
MX25L1608D@WSON8 [DX4005#1]
MX25L1608E@SOP8(150mil) [DX1045#1]
MX25L1608E@SOP8(200mil) [DX1044#1]
MX25L1615D@SOP16 [DX1033#1]
MX25L1615D@SOP8 [DX1044#1]
MX25L1633E@SOP16 [DX1033#1]
MX25L1633E@SOP8 [DX1044#1]
MX25L1633E@WSON8 [DX4005#1]
MX25L1635D@SOP16 [DX1033#1]
MX25L1635D@SOP8(150mil) [DX1045#1]
MX25L1635D@SOP8(200mil) [DX1044#1]
MX25L1635D@WSON8 [DX4005#1]
MX25L1635E@SOP8 [DX1044#1]
MX25L1636D@SOP16 [DX1033#1]
MX25L1636D@SOP8(150mil) [DX1045#1]
MX25L1636D@SOP8(200mil) [DX1044#1]
MX25L1636D@WSON8 [DX4005#1]
MX25L1636E@SOP8 [DX1044#1]
MX25L1655D@SOP8 [DX1044#1]
MX25L1655D@SOP8[512 bit] [DX1044#1]
MX25L1655D@TBGA24 [DX5146]
MX25L1655D@TBGA24[512 bit] [DX5146]
MX25L1673E@SOP8 [DX1044#1]
MX25L1675E@SOP8 [DX1044#1]
MX25L1675E@WSON8 [DX4005#1]
MX25L2005 [DX0001]
MX25L2005(ISP) [DX0001]
MX25L2005@SON8 [DX4005]
MX25L2005@SON8(ISP) [DX0001]
MX25L2005@SOP8 [DX1045]
MX25L2005@SOP8(ISP) [DX0001]
MX25L2005C@SOP8 [DX1045]

MX25L2005C@USON8 [DX4005]
MX25L2006E@SOP8 [DX1045#1]
MX25L2006E@WSON8 [DX4005#1]
MX25L2025 [DX0001]
MX25L2025@SON8 [DX4005#1]
MX25L2025@SOP8 [DX1045#1]
MX25L2026C@SOP8 [DX1045#1]
MX25L2026E@SOP8 [DX1045#1]
MX25L2026E@WSON8 [DX4005#1]
MX25L25635E@SOP16 [DX1072#1]
MX25L25635E@WSON8 [DX4006#1]
MX25L25635F@SOP16 [DX1072#1]
MX25L25635F@WSON8 [DX4006#1]
MX25L25636E@SOP16 [DX1072#1]
MX25L25639F@WSON8 [DX4006#1]
MX25L25645G@BGA24[4*6] [DX5146]
MX25L25645G@BGA24[5*5] [DX5157]
MX25L25645G@SOP16 [DX1072#1]
MX25L25645G@SOP8 [DX1044#1]
MX25L25645G@WSON8 [DX4006#1]
MX25L25655E@SOP16 [DX1072#1]
MX25L25655E@TFBGA24 [DX5146]
MX25L25655F@SOP16 [DX1072#1]
MX25L25655F@TFBGA24[4*6] [DX5146]
MX25L25655F@TFBGA24[5*5] [DX5157]
MX25L25735E@SOP16 [DX1072#1]
MX25L25735E@WSON8 [DX4006#1]
MX25L25735F@SOP16 [DX1072#1]
MX25L25735F@WSON8 [DX4006#1]
MX25L25835E@SOP16 [DX1072#1]
MX25L3205@SOP16 [DX1033#1]
MX25L3205@SOP16(Fast Mode) [DX1033#1]
MX25L3205@SOP8 [DX1044#1]
MX25L3205@SOP8(Fast Mode) [DX1044#1]
MX25L3205A@SON8 [DX4006#1]
MX25L3205A@SON8(Fast Mode) [DX4006#1]
MX25L3205A@SOP16 [DX1033#1]
MX25L3205A@SOP16(Fast Mode) [DX1033#1]
MX25L3205A@SOP8 [DX1044#1]
MX25L3205A@SOP8(Fast Mode) [DX1044#1]
MX25L3205D(512bit OTP) [DX0001]
MX25L3205D@SON8(Fast Mode) [DX4006#1]
MX25L3205D@SOP16 [DX1033#1]
MX25L3205D@SOP16(512bit OTP) [DX1072#1]
MX25L3205D@SOP16(Fast Mode) [DX1033#1]
MX25L3205D@SOP8 [DX1044#1]
MX25L3205D@SOP8(512bit OTP) [DX1044#1]
MX25L3205D@SOP8(Fast Mode) [DX1044#1]
MX25L3205D@USON8 [DX4004#1]
MX25L3205D@USON8(512bit OTP) [DX4004#1]
MX25L3205D@USON8(Fast Mode) [DX4004#1]
MX25L3205D@WSON8(512bit OTP) [DX4005#1]
MX25L3206E [DX1044#1]
MX25L3206E(512bit) [DX0001]
MX25L3206E(512bit)@SOIC16 [DX1072#1]
MX25L3206E(512bit)@SOIC8 [DX1044#1]
MX25L3206E(512bit)@USON8 [DX4004#1]
MX25L3206E(512bit)@WSON8 [DX4005#1]
MX25L3206E@SOP16 [DX1072#1]
MX25L3206E@SOP8 [DX1044#1]
MX25L3206E@USON8 [DX4004#1]
MX25L3206E@WSON8 [DX4005#1]
MX25L3208D [DX0001]
MX25L3208D@SOP16 [DX1072#1]
MX25L3208D@SOP8 [DX1044#1]
MX25L3208D@USON8 [DX4004#1]
MX25L3208D@WSON8 [DX4005#1]
MX25L3208E@SOP8 [DX1044#1]

MX25L3215D@SOP16 [DX1033#1]
MX25L3215D@SOP8 [DX1044#1]
MX25L3225D@SOP8 [DX1044#1]
MX25L3233F [DX1044#1]
MX25L3233F@SOP16 [DX1072#1]
MX25L3233F@SOP8(150 mil) [DX1044#1]
MX25L3233F@SOP8(200 mil) [DX1044#1]
MX25L3233F@USON8 [DX4004#1]
MX25L3233F@WSON8 [DX4005#1]
MX25L3235D@SOP16 [DX1033#1]
MX25L3235D@SOP8 [DX1044#1]
MX25L3235D@WSON8 [DX4005#1]
MX25L3235E@SOP8 [DX1044#1]
MX25L3235E@WSON8 [DX4005#1]
MX25L3236D@SOP16 [DX1033#1]
MX25L3236D@SOP8(150mil) [DX1045#1]
MX25L3236D@SOP8(200mil) [DX1044#1]
MX25L3236D@WSON8 [DX4005#1]
MX25L3237D@SOP16 [DX1033#1]
MX25L3237D@WSON8 [DX4005#1]
MX25L3239E@SOP8 [DX1044#1]
MX25L3239E@VSOP8 [DX1044#1]
MX25L3239E@WSON8 [DX4005#1]
MX25L3254E@SOP8[4K bit] [DX1044#1]
MX25L3254E@TFBGA24[5*5] [DX5157]
MX25L3254E@TFBGA24[6*4] [DX5146]
MX25L3255D@SOP8 [DX1044#1]
MX25L3255D@SOP8[4K bit] [DX1044#1]
MX25L3255D@TBGA24 [DX5146]
MX25L3255D@TBGA24[4K bit] [DX5146]
MX25L3255E@SOP8 [DX1044#1]
MX25L3255E@SOP8[4K bit] [DX1044#1]
MX25L3255E@TBGA24 [DX5146]
MX25L3255E@TFBGA24[5*5] [DX5157]
MX25L3255E@TFBGA24[6*4] [DX5146]
MX25L3273E@SOP16 [DX1033#1]
MX25L3273E@SOP8 [DX1044#1]
MX25L3273E@VSOP8 [DX1044#1]
MX25L3273E@WSON8 [DX4005#1]
MX25L3275E@SOP16 [DX1033#1]
MX25L3275E@SOP8 [DX1044#1]
MX25L3275E@WSON8 [DX4005#1]
MX25L4005 [DX0001]
MX25L4005(150mil)@SOP8 [DX1045]
MX25L4005(150mil)@SOP8(ISP) [DX0001]
MX25L4005(209mil)@SOP8 [DX1044]
MX25L4005(209mil)@SOP8(ISP) [DX0001]
MX25L4005(ISP) [DX0001]
MX25L4005@SON8 [DX4005]
MX25L4005@SON8(ISP) [DX0001]
MX25L4005A [DX0001]
MX25L4005A(150mil)@SOP8 [DX1045]
MX25L4005A(150mil)@SOP8(ISP) [DX0001]
MX25L4005A(209mil)@SOP8 [DX1044]
MX25L4005A(209mil)@SOP8(ISP) [DX0001]
MX25L4005A(ISP) [DX0001]
MX25L4005A@SON8 [DX4005]
MX25L4005A@SON8(ISP) [DX0001]
MX25L4005A@USON8 [DX4004]
MX25L4005C [DX0001]
MX25L4005C@SOP8 [DX1045]
MX25L4005C@TSSOP8 [DX1044]
MX25L4005C@USON8 [DX4005]
MX25L4006E [DX0001]
MX25L4006E@SOP8(150 mil) [DX1045#1]
MX25L4006E@SOP8(200 mil) [DX1044#1]
MX25L4006E@USON8 [DX4002#1]
MX25L4006E@WSON8 [DX4005#1]
MX25L4006EG@SOP8(200 mil) [DX1044#1]
MX25L4025@SOP8 [DX1045]
MX25L4025A [DX0001]
MX25L4025A(150mil)@SOP8 [DX1045#1]

MX25L4025A(209mil)@SOP8 [DX1044#1]
MX25L4025A@SON8 [DX4005#1]
MX25L4026D@SOP8 [DX1045#1]
MX25L4026E@SOP8 [DX1045#1]
MX25L512@SON8 [DX4005#1]
MX25L512@SOP8 [DX1045#1]
MX25L512@USON8 [DX4002#1]
MX25L5121E@SOP8 [DX1045#1]
MX25L5121E@TSSOP8 [DX1059#1]
MX25L512A [DX0001]
MX25L512A@SON8 [DX4005#1]
MX25L512A@SOP8 [DX1045#1]
MX25L512C [DX0001]
MX25L512C@TSSOP8 [DX1059#3]
MX25L512C@USON8 [DX4002#1]
MX25L512E@SOP8 [DX1045#1]
MX25L512E@TSSOP8 [DX1059#1]
MX25L512E@USON8 [DX4002#1]
MX25L6405@SOP16 [DX1033#1]
MX25L6405@SOP16(Fast Mode) [DX1033#1]
MX25L6405@SOP8 [DX1044#1]
MX25L6405@SOP8(Fast Mode) [DX1044#1]
MX25L6405D@SON8(Fast Mode) [DX4006#1]
MX25L6405D@SOP16 [DX1033#1]
MX25L6405D@SOP16(512bit OTP) [DX1072#1]
MX25L6405D@SOP16(Fast Mode) [DX1033#1]
MX25L6405D@SOP8 [DX1044#1]
MX25L6405D@WSON8(512bit OTP) [DX4006#1]
MX25L6405MC@SOP16 [DX1033#1]
MX25L6405MC@SOP8 [DX1044#1]
MX25L6406E@SOP16 [DX1072#1]
MX25L6406E@SOP8 [DX1044#1]
MX25L6406E@TFBGA24(4*6) [DX5146]
MX25L6406E@TFBGA24(5*5) [DX5157]
MX25L6406E@WSON8 [DX4006#1]
MX25L6408D@SOP16 [DX1072#1]
MX25L6408D@WSON8 [DX4006#1]
MX25L6408E@SOP16 [DX1072#1]
MX25L6408E@SOP8 [DX1044#1]
MX25L6415D@SOP16 [DX1033#1]
MX25L6415D@SOP8 [DX1044#1]
MX25L6433F@SOP16 [DX1072#1]
MX25L6433F@SOP8 [DX1044#1]
MX25L6433F@TFBGA24(4*6) [DX5146]
MX25L6433F@TFBGA24(5*5) [DX5157]
MX25L6433F@WSON8 [DX4006#1]
MX25L6435E@SOP8 [DX1044#1]
MX25L6435E@WSON8 [DX4006#1]
MX25L6436E@SOP16 [DX1033#1]
MX25L6436E@SOP8 [DX1044#1]
MX25L6436E@WSON8 [DX4006#1]
MX25L6439F@SOP8 [DX1044#1]
MX25L6439F@VSOP8 [DX1044#1]
MX25L6445E@SOP16 [DX1033#1]
MX25L6445E@SOP16(4K bit OTP) [DX1033#1]
MX25L6445E@SOP8 [DX1044#1]
MX25L6445E@SOP8(4K bit OTP) [DX1044#1]
MX25L6445E@WSON8 [DX4006#1]
MX25L6445E@WSON8(4K bit OTP) [DX4006#1]
MX25L6446E@SOP16 [DX1033#1]
MX25L6446E@SOP8 [DX1044#1]
MX25L6446E@WSON8 [DX4006#1]
MX25L6455E@SOP16 [DX1033#1]
MX25L6455E@SOP8 [DX1044#1]
MX25L6455E@TFBGA24 [DX5146]
MX25L6456E@SOP8 [DX1044#1]
MX25L6456E@TFBGA24(4*6) [DX5146]
MX25L6456E@TFBGA24(5*5) [DX5157]
MX25L6465E@SOP16 [DX1033#1]
MX25L6465E@SOP8 [DX1044#1]
MX25L6465E@WSON8 [DX4006#1]
MX25L6473E@SOP16 [DX1033#1]
MX25L6473E@SOP8 [DX1044#1]
MX25L6473E@VSOP8 [DX1044#1]
MX25L6473E@WSON8 [DX4005#1]
MX25L6475E@SOP16 [DX1033#1]
MX25L6475E@SOP8 [DX1044#1]
MX25L6475E@WSON8 [DX4005#1]
MX25L8005 [DX0001]
MX25L8005(150mil)@SOP8 [DX1045]

MX25L8005(150mil)@SOP8(ISP) [DX0001]
MX25L8005(209mil)@SOP8 [DX1044]
MX25L8005(209mil)@SOP8(ISP) [DX0001]
MX25L8005(ISP) [DX0001]
MX25L8005@SON8 [DX4005]
MX25L8005@SON8(ISP) [DX0001]
MX25L8005@USON8 [DX4004]
MX25L8006E [DX0001]
MX25L8006E(512bit) [DX0001]
MX25L8006E(512bit)@SOIC8(150mil) [DX1045#1]
MX25L8006E(512bit)@SOIC8(200mil) [DX1044#1]
MX25L8006E(512bit)@USON8 [DX4004#1]
MX25L8006E(512bit)@WSON8 [DX4005#1]
MX25L8006E@SOP8(150 mil) [DX1045#1]
MX25L8006E@SOP8(200 mil) [DX1044#1]
MX25L8006E@SOP8(DELTA) [DX1045#1]
MX25L8006E@USON8 [DX4004#1]
MX25L8006E@WSON8 [DX4005#1]
MX25L8006EG@SOP8(200 mil) [DX1044#1]
MX25L8025 [DX0001]
MX25L8025(150mil)@SOP8 [DX1045#1]
MX25L8025(209mil)@SOP8 [DX1044#1]
MX25L8025@SON8 [DX4005#1]
MX25L8035E@SOP8 [DX1044#1]
MX25L8036D [DX0001]
MX25L8036D@SOP16 [DX1033]
MX25L8036D@SOP8(150mil) [DX1045]
MX25L8036D@SOP8(200mil) [DX1044]
MX25L8036D@WSON8 [DX4005]
MX25L8036E@SOP8 [DX1044#1]
MX25L8073E@SOP8 [DX1044#1]
MX25L8075E@SOP8 [DX1044#1]
MX25R3233F@SOP8 [DX1045#1]
MX25R3233F@USON8 [DX4004#1]
MX25R3233F@WSON8 [DX4005#1]
MX25R3235F@SOP8 [DX1045#1]
MX25R3235F@USON8 [DX4004#1]
MX25R3235F@WSON8 [DX4005#1]
MX25R6435F@SOP8 [DX1044#1]
MX25R6435F@USON8 [DX4004#1]
MX25R6435F@WSON8 [DX4005#1]
MX25U12835F@SOP16 [DX1033#1]
MX25U12835F@USON8 [DX4005#1]
MX25U12835F@WSON8 [DX4006#1]
MX25U1631@USON8(4*3mm) [DX4081#1]
MX25U1631@USON8(4*4mm) [DX4004#1]
MX25U1631@USON8(6*5mm) [DX4005#1]
MX25U1635@SOIC8 [DX1045#1]
MX25U1635@USON8(4*3mm) [DX4081#1]
MX25U1635@USON8(4*4mm) [DX4004#1]
MX25U1635@USON8(6*5mm) [DX4005#1]
MX25U1635E@SOP8(150mil) [DX1045#1]
MX25U1635E@SOP8(200mil) [DX1044#1]
MX25U1635E@USON8 [DX4004#1]
MX25U1635E@WSON8 [DX4005#1]
MX25U2032E@SOP8 [DX1045#1]
MX25U2032E@USON8 [DX4004#1]
MX25U2032E@WSON8 [DX4005#1]
MX25U2033E@SOP8 [DX1045#1]
MX25U2033E@USON8 [DX4004#1]
MX25U2033E@WSON8 [DX4005#1]
MX25U25635E@SOP16 [DX1072#1]
MX25U25635E@WSON8 [DX4006#1]
MX25U25635F@SOP16 [DX1072#1]
MX25U25635F@WSON8 [DX4006#1]
MX25U3235E@SOP8(150mil) [DX1045#1]
MX25U3235E@SOP8(200mil) [DX1044#1]
MX25U3235E@USON8 [DX4004#1]
MX25U3235E@WSON8 [DX4005#1]
MX25U3235F@SOP8 [DX1044#1]
MX25U3235F@WSON8 [DX4005#1]

MX25U4032E@SOP8 [DX1045#1]
MX25U4032E@USON8 [DX4004#1]
MX25U4032E@WSON8 [DX4005#1]
MX25U4033E@SOP8 [DX1045#1]
MX25U4033E@TSSOP8 [DX1059#1]
MX25U4033E@USON8 [DX4004#1]
MX25U4033E@WSON8 [DX4005#1]
MX25U4035@SOIC8 [DX1045#1]
MX25U4035@USON8(4*4mm) [DX4004#1]
MX25U4035@USON8(6*5mm) [DX4005#1]
MX25U6435E@WSON8 [DX4005#1]
MX25U6435F@SOP8 [DX1044#1]
MX25U6435F@WSON8 [DX4005#1]
MX25U6439F@SOP8 [DX1044#1]
MX25U6439F@VSOP8 [DX1044#1]
MX25U6439F@WSON8 [DX4005#1]
MX25U6473F@SOP8 [DX1044#1]
MX25U8032E@SOP8(150mil) [DX1045#1]
MX25U8032E@SOP8(200mil) [DX1044#1]
MX25U8032E@USON8(4*3) [DX4081#1]
MX25U8032E@USON8(4*4) [DX4004#1]
MX25U8032E@WSON8 [DX4005#1]
MX25U8033E@SOP8(150mil) [DX1045#1]
MX25U8033E@SOP8(200mil) [DX1044#1]
MX25U8033E@USON8(4*3) [DX4081#1]
MX25U8033E@USON8(4*4) [DX4004#1]
MX25U8033E@WSON8 [DX4005#1]
MX25U8035@SOIC8 [DX1045#1]
MX25U8035@USON8(4*4mm) [DX4004#1]
MX25U8035@USON8(6*5mm) [DX4005#1]
MX25U8035E@SOP8(150mil) [DX1045#1]
MX25U8035E@SOP8(200mil) [DX1044#1]
MX25U8035E@USON8 [DX4004#1]
MX25U8035E@WSON8 [DX4005#1]
MX25V1006E@TSSOP8 [DX1059#1]
MX25V1006E@USON8 [DX4002#1]
MX25V2006E@SOP8 [DX1045#1]
MX25V2006E@WSON8 [DX4005#1]
MX25V4005 [DX0001]
MX25V4005@USON8 [DX4005]
MX25V4005C@SOP8 [DX0001]
MX25V4005C@WSON8 [DX4005]
MX25V4006E@SOP8 [DX1045#1]
MX25V4006E@USON8 [DX4002#1]
MX25V4006E@WSON8 [DX4005#1]
MX25V4035@SOP8 [DX1045#1]
MX25V4035@WSON8 [DX4005#1]
MX25V512@USON8 [DX4002#1]
MX25V512C@TSSOP8 [DX1059#3]
MX25V512C@USON8 [DX4002#1]
MX25V512E@SOP8 [DX1045#1]
MX25V512E@USON8 [DX4002#1]
MX25V6433F@SOP8 [DX1044#1]
MX25V6433F@VSOP8 [DX1044#1]
MX25V6433F@WSON8 [DX4005#1]
MX25V8005@SOP8 [DX1045]
MX25V8005@WSON8 [DX4005]
MX25V8006E(512bit)@SOIC8 [DX1045#1]
MX25V8006E(512bit)@WSON8 [DX4005#1]
MX25V8006E@SOP8 [DX1045#1]
MX25V8006E@WSON8 [DX4005#1]
MX25V8035@SOP8 [DX1045#1]
MX25V8035@WSON8 [DX4005#1]
MX26C1000 [DX0001]
MX26C1000@PLCC32 [DX2032]
MX26C1000@SOIC32 [DX1034]
MX26C1000@TSOP32 [DX1002]
MX26C1000B [DX0001]
MX26C1000B@PLCC32 [DX2032]
MX26C1000B@SOIC32 [DX1019]
MX26C1000B@TSOP32 [DX1002]
MX26C2000B [DX0001]
MX26C2000B@PLCC32 [DX2032]
MX26C2000B@SOIC32 [DX1019]
MX26C2000B@TSOP32 [DX1002]
MX26C512A [DX0001]
MX26C512A@PLCC32 [DX2032]
MX26C512A@SOIC28 [DX1035]
MX26C512A@TSOP28 [DX1024]
MX26F128J3TC@TSOP56 [DX1011]
MX26F128J3XC@CSP64 [DX5004]

MX26F640J3TC@TSOP56 [DX1055]
MX26F640J3XC@CSP64 [DX5004]
MX26L12711MC@PSOP44 [DX1014]
MX26L12811MC@PSOP44 [DX1014]
MX26L6419T@TSOP48 [DX1004]
MX26L6420@PSOP44 [DX1014]
MX26L6420@TSOP48 [DX1001]
MX26LV004B@PLCC32 [DX2032]
MX26LV004B@TSOP40 [DX1006]
MX26LV004T@PLCC32 [DX2032]
MX26LV004T@TSOP40 [DX1006]
MX26LV008B@TSOP40 [DX1006]
MX26LV008T@TSOP40 [DX1006]
MX26LV040 [DX0001]
MX26LV040@PLCC32 [DX2032]
MX26LV040@TSOP32 [DX1002]
MX26LV160BT@TSOP48 [DX1043]
MX26LV160BX(0.3)@CSP48 [DX5002]
MX26LV160BX(0.4)@CSP48 [DX5002]
MX26LV160TT@TSOP48 [DX1043]
MX26LV160TX(0.3)@CSP48 [DX5002]
MX26LV160TX(0.4)@CSP48 [DX5002]
MX26LV400BT@TSOP48 [DX1043]
MX26LV400BX(0.3)@CSP48 [DX5002]
MX26LV400BX(0.4)@CSP48 [DX5002]
MX26LV400TT@TSOP48 [DX1043]
MX26LV400TX(0.3)@CSP48 [DX5002]
MX26LV400TX(0.4)@CSP48 [DX5002]
MX26LV800BM@PSOP44 [DX1014]
MX26LV800BT@TSOP48 [DX1043]
MX26LV800BX(0.3)@CSP48 [DX5002]
MX26LV800BX(0.4)@CSP48 [DX5002]
MX26LV800TM@PSOP44 [DX1014]
MX26LV800TT@TSOP48 [DX1043]
MX26LV800TX(0.3)@CSP48 [DX5002]
MX26LV800TX(0.4)@CSP48 [DX5002]
MX27C1000 [DX0001]
MX27C1000@PLCC32 [DX2032]
MX27C1000@SOIC32 [DX1034]
MX27C1000@TSOP32 [DX1002]
MX27C1000A [DX0001]
MX27C1000A@PLCC32 [DX2032]
MX27C1000A@SOIC32 [DX1034]
MX27C1000A@TSOP32 [DX1002]
MX27C1001 [DX0001]
MX27C1001@PLCC32 [DX2032]
MX27C1001@SOIC32 [DX1034]
MX27C1001@TSOP32 [DX1002]
MX27C1024 [DX0001]
MX27C1024@PLCC44 [DX2044]
MX27C1024@SOP40 [DX1022]
MX27C1024@VSOP40 [DX1005]
MX27C1024A [DX0001]
MX27C1024A@PLCC44 [DX2044]
MX27C1024A@SOP40 [DX1022]
MX27C1024A@VSOP40 [DX1005]
MX27C1024B [DX0001]
MX27C1024B@PLCC44 [DX2044]
MX27C1024B@SOP40 [DX1022]
MX27C1024B@VSOP40 [DX1005]
MX27C1100 [DX0001]
MX27C1610 [DX0001]
MX27C2000 [DX0001]
MX27C2000@PLCC32 [DX2032]
MX27C2000@SOIC32 [DX1034]
MX27C2000@TSOP32 [DX1002]
MX27C2000A [DX0001]
MX27C2000A@PLCC32 [DX2032]
MX27C2000A@SOIC32 [DX1034]
MX27C2000A@TSOP32 [DX1002]
MX27C2048 [DX0001]
MX27C2048@PLCC44 [DX2044]
MX27C2048@VSOP40 [DX1005]
MX27C2100 [DX0001]
MX27C256 [DX0001]
MX27C256@PLCC32 [DX2032]
MX27C4000 [DX0001]
MX27C4000@PLCC32 [DX2032]
MX27C4000@SOIC32 [DX1034]
MX27C4000@TSOP32 [DX1002]
MX27C4000A [DX0001]
MX27C4000A@PLCC32 [DX2032]
MX27C4000A@SOIC32 [DX1034]
MX27C4000A@TSOP32 [DX1002]
MX27C4096 [DX0001]
MX27C4096@PLCC44 [DX2044]
MX27C4100 [DX0001]
MX27C4111 [DX0001]
MX27C512 [DX0001]
MX27C512@PLCC32 [DX2032]
MX27C516 [DX0001]
MX27C516@PLCC44 [DX2044]
MX27C516@VSOP40 [DX1005]
MX27C8000 [DX0001]
MX27C8000@PLCC32 [DX2032]
MX27C8000@SOIC32 [DX1034]

MX27C8000@TSOP32 [DX1002]
MX27C8000A [DX0001]
MX27C8000A@PLCC32 [DX2032]
MX27C8000A@SOIC32 [DX1034]
MX27C8000A@TSOP32 [DX1002]
MX27C8100 [DX0001]
MX27C8100@PSOP44 [DX1014]
MX27C8111 [DX0001]
MX27C8111@PSOP44 [DX1014]
MX27L1000 [DX0001]
MX27L1000@PLCC32 [DX2032]
MX27L1000@TSOP32 [DX1002]
MX27L2000 [DX0001]
MX27L2000@PLCC32 [DX2032]
MX27L2000@TSOP32 [DX1002]
MX27L256 [DX0001]
MX27L256@PLCC32 [DX2032]
MX27L256@TSOP32 [DX1024]
MX27L4000 [DX0001]
MX27L4000@PLCC32 [DX2032]
MX27L4000@TSOP32 [DX1002]
MX27L4096 [DX0001]
MX27L4096@PLCC44 [DX2044]
MX27L512 [DX0001]
MX27L512@PLCC32 [DX2032]
MX27L512@TSOP28 [DX1024]
MX28F002B@TSOP40 [DX1006]
MX28F002T@TSOP40 [DX1006]
MX28F1000 [DX0001]
MX28F1000(REVERSE)@TSOP32 [DX1002]
MX28F1000@PLCC32 [DX2032]
MX28F1000@SOP32 [DX1019]
MX28F1000@TSOP32 [DX1002]
MX28F1000P [DX0001]
MX28F1000P(REVERSE)@TSOP32 [DX1002]
MX28F1000P@PLCC32 [DX2032]
MX28F1000P@TSOP32 [DX1002]
MX28F160C3BT@TSOP48 [DX1004]
MX28F160C3BX@uBGA48 [DX50UN]
MX28F160C3TT@TSOP48 [DX1004]
MX28F160C3TX@uBGA48 [DX50UN]
MX28F2000 [DX0001]
MX28F2000(REVERSE)@TSOP32 [DX1002]
MX28F2000@PLCC32 [DX2032]
MX28F2000@TSOP32 [DX1002]
MX28F2000P [DX0001]
MX28F2000P(REVERSE)@TSOP32 [DX1002]
MX28F2000P@PLCC32 [DX2032]
MX28F2000P@TSOP32 [DX1002]
MX28F2100B@PSOP44 [DX1014]
MX28F2100B@TSOP48 [DX1004]
MX28F2100T@PSOP44 [DX1014]
MX28F2100T@TSOP48 [DX1004]
MX28F4000 [DX0001]
MX28F4000@PLCC32 [DX2032]
MX28F4000@SOP32 [DX1019]
MX28F4000@TSOP32 [DX1002]
MX28F640C3BT@TSOP48 [DX1004]
MX28F640C3BX@uBGA48 [DX50UN]
MX28F640C3TT@TSOP48 [DX1004]
MX28F640C3TX@uBGA48 [DX50UN]
MX29F001B [DX0001]
MX29F001B@PLCC32 [DX2032]
MX29F001B@TSOP32 [DX1002]
MX29F001T [DX0001]
MX29F001T@PLCC32 [DX2032]
MX29F001T@TSOP32 [DX1002]
MX29F002B [DX0001]
MX29F002B@PLCC32 [DX2032]
MX29F002B@TSOP32 [DX1002]
MX29F002NB [DX0001]
MX29F002NB@PLCC32 [DX2032]
MX29F002NB@TSOP32 [DX1002]
MX29F002NT [DX0001]
MX29F002NT@PLCC32 [DX2032]
MX29F002NT@TSOP32 [DX1002]
MX29F002T [DX0001]
MX29F002T@PLCC32 [DX2032]
MX29F002T@TSOP32 [DX1002]
MX29F004B [DX0001]
MX29F004B@PLCC32 [DX2032]
MX29F004B@TSOP32 [DX1002]
MX29F004T [DX0001]
MX29F004T@PLCC32 [DX2032]
MX29F004T@TSOP32 [DX1002]
MX29F016(REVERSE)@TSOP40 [DX1006]
MX29F016(REVERSE)@TSOP48 [DX1004]

MX29F016@PSOP44 [DX1014]
MX29F016@TSOP40 [DX1006]
MX29F016@TSOP48 [DX1004]
MX29F022B [DX0001]
MX29F022B@PLCC32 [DX2032]
MX29F022B@TSOP32 [DX1002]
MX29F022NB [DX0001]
MX29F022NB@PLCC32 [DX2032]
MX29F022NB@TSOP32 [DX1002]
MX29F022NT [DX0001]
MX29F022NT@PLCC32 [DX2032]
MX29F022NT@TSOP32 [DX1002]
MX29F022T [DX0001]
MX29F022T@PLCC32 [DX2032]
MX29F022T@TSOP32 [DX1002]
MX29F040 [DX0001]
MX29F040@PLCC32 [DX2032]
MX29F040@TSOP32 [DX1002]
MX29F040C [DX0001]
MX29F040C@PLCC32 [DX2032]
MX29F040C@TSOP32 [DX1002]
MX29F080(REVERSE)@TSOP40 [DX1006]
MX29F080@PSOP44 [DX1014]
MX29F080@TSOP40 [DX1006]
MX29F100B@PSOP44 [DX1014]
MX29F100B@TSOP48 [DX1004]
MX29F100T@PSOP44 [DX1014]
MX29F100T@TSOP48 [DX1004]
MX29F1610@PSOP44 [DX1014]
MX29F1610@TSOP48 [DX1004]
MX29F1610A@PSOP44 [DX1014]
MX29F1610A@TSOP48 [DX1004]
MX29F1610B@TSOP48 [DX1004]
MX29F1611@PSOP44 [DX1014]
MX29F1615 [DX0001]
MX29F200B(REVERSE)@TSOP48 [DX1004]
MX29F200B@PSOP44 [DX1014]
MX29F200B@TSOP48 [DX1004]
MX29F200CB@PSOP44 [DX1014]
MX29F200CB@TSOP48 [DX1043]
MX29F200CT@PSOP44 [DX1014]
MX29F200CT@TSOP48 [DX1043]
MX29F200T(REVERSE)@TSOP48 [DX1004]
MX29F200T@PSOP44 [DX1014]
MX29F200T@TSOP48 [DX1004]
MX29F4000 [DX0001]
MX29F400B(REVERSE)@TSOP48 [DX1004]
MX29F400B@PSOP44 [DX1014]
MX29F400B@TSOP48 [DX1004]
MX29F400CB@PSOP44 [DX1014]
MX29F400CB@TSOP48 [DX1043]
MX29F400CT@PSOP44 [DX1014]
MX29F400CT@TSOP48 [DX1043]
MX29F400T(REVERSE)@TSOP48 [DX1004]
MX29F400T@PSOP44 [DX1014]
MX29F400T@TSOP48 [DX1004]
MX29F800B(REVERSE)@TSOP48 [DX1004]
MX29F800B@PSOP44 [DX1014]
MX29F800B@TSOP48 [DX1004]
MX29F800CBM@PSOP44 [DX1014]
MX29F800CBT@TSOP48 [DX1043]
MX29F800CBXB@FBGA48 [DX5002]
MX29F800CTM@PSOP44 [DX1014]
MX29F800CTT@TSOP48 [DX1043]
MX29F800CTXB@FBGA48 [DX5002]
MX29F800T(REVERSE)@TSOP48 [DX1004]
MX29F800T@PSOP44 [DX1014]
MX29F800T@TSOP48 [DX1004]
MX29F8100@PSOP44 [DX1014]
MX29F8100@TSOP48 [DX1004]
MX29GA128EHXC@FBGA64 [DX5004]
MX29GA128EHXF@FBGA64 [DX5074]
MX29GA128ELXC@FBGA64 [DX5004]
MX29GA128ELXF@FBGA64 [DX5074]
MX29GA129EHXC@FBGA64 [DX5004]
MX29GA129EHXF@FBGA64 [DX5074]
MX29GA129ELXC@FBGA64 [DX5004]
MX29GA129ELXF@FBGA64 [DX5074]
MX29GA256EHXC@FBGA64 [DX5004]
MX29GA256EHXF@FBGA64 [DX5074]
MX29GA256ELXC@FBGA64 [DX5004]
MX29GA256ELXF@FBGA64 [DX5074]
MX29GA256FHXF@FBGA64 [DX5074]
MX29GA256FLXF@FBGA64 [DX5074]
MX29GA257EHXC@FBGA64 [DX5004]
MX29GA257EHXF@FBGA64 [DX5074]

MX29GA257ELXC@FBGA64 [DX5004]
MX29GA257ELXF@FBGA64 [DX5074]
MX29GA257FHXC@FBGA64 [DX5004]
MX29GA257FLXC@FBGA64 [DX5004]
MX29GA320EHXF@FBGA64 [DX5074]
MX29GA320ELXF@FBGA64 [DX5074]
MX29GA321EHXC@FBGA64 [DX5004]
MX29GA321ELXC@FBGA64 [DX5004]
MX29GA512FHXF@FBGA64 [DX5074]
MX29GA512FLXF@FBGA64 [DX5074]
MX29GA640EHXF@FBGA64 [DX5074]
MX29GA640ELXF@FBGA64 [DX5074]
MX29GA641EHXC@FBGA64 [DX5004]
MX29GA641ELXC@FBGA64 [DX5004]
MX29GL128EDT2@TSOP56 [DX1011]
MX29GL128EDXF@FBGA64 [DX5074]
MX29GL128EHT2@TSOP56 [DX1011]
MX29GL128EHXC@FBGA64 [DX5004]
MX29GL128EHXF@FBGA64 [DX5074]
MX29GL128ELT2@TSOP56 [DX1011]
MX29GL128ELXC@FBGA64 [DX5004]
MX29GL128ELXF@FBGA64 [DX5074]
MX29GL128EUT2@TSOP56 [DX1011]
MX29GL128EUXF@FBGA64 [DX5074]
MX29GL128FDT2@TSOP56 [DX1011]
MX29GL128FDXF@FBGA64 [DX5074]
MX29GL128FDXG@FBGA56 [DX5045]
MX29GL128FHT2@TSOP56 [DX1011]
MX29GL128FHXF@FBGA64 [DX5074]
MX29GL128FHXG@FBGA56 [DX5045]
MX29GL128FLT2@TSOP56 [DX1011]
MX29GL128FLXF@FBGA64 [DX5074]
MX29GL128FLXG@FBGA56 [DX5045]
MX29GL128FUT2@TSOP56 [DX1011]
MX29GL128FUXF@FBGA64 [DX5074]
MX29GL128FUXG@FBGA56 [DX5045]
MX29GL256EDT2@TSOP56 [DX1011]
MX29GL256EDXF@FBGA64 [DX5074]
MX29GL256EHT2@TSOP56 [DX1011]
MX29GL256EHXC@FBGA64 [DX5004]
MX29GL256EHXF@FBGA64 [DX5074]
MX29GL256ELT2@TSOP56 [DX1011]
MX29GL256ELXC@FBGA64 [DX5004]
MX29GL256ELXF@FBGA64 [DX5074]
MX29GL256ES@SSOP56 [DX1057]
MX29GL256EUT2@TSOP56 [DX1011]
MX29GL256EUXF@FBGA64 [DX5074]
MX29GL256FDT2@TSOP56 [DX1011]
MX29GL256FDXF@FBGA64 [DX5074]
MX29GL256FDXG@FBGA56 [DX5045]
MX29GL256FHT2@TSOP56 [DX1011]
MX29GL256FHXF@FBGA64 [DX5074]
MX29GL256FHXG@FBGA56 [DX5045]
MX29GL256FLT2@TSOP56 [DX1011]
MX29GL256FLXF@FBGA64 [DX5074]
MX29GL256FLXG@FBGA56 [DX5045]
MX29GL256FUT2@TSOP56 [DX1011]
MX29GL256FUXF@FBGA64 [DX5074]
MX29GL256FUXG@FBGA56 [DX5045]
MX29GL320EB@TSOP48 [DX1004]
MX29GL320EBXE@FBGA48 [DX5002]
MX29GL320EHT2@TSOP56 [DX1011]
MX29GL320EHXF@FBGA64 [DX5074]
MX29GL320ELT2@TSOP56 [DX1011]
MX29GL320ELXF@FBGA64 [DX5074]
MX29GL320ET@TSOP48 [DX1004]
MX29GL320ETXE@FBGA48 [DX5002]
MX29GL512EHT2@TSOP56 [DX1011]
MX29GL512EHXF@FBGA64 [DX5074]
MX29GL512ELT2@TSOP56 [DX1011]
MX29GL512ELXF@FBGA64 [DX5074]
MX29GL512FDT2@TSOP56 [DX1011]
MX29GL512FDXF@FBGA64 [DX5074]
MX29GL512FHT2@TSOP56 [DX1011]
MX29GL512FHXF@FBGA64 [DX5074]
MX29GL512FLT2@TSOP56 [DX1011]
MX29GL512FLXF@FBGA64 [DX5074]
MX29GL512FUT2@TSOP56 [DX1011]
MX29GL512FUXF@FBGA64 [DX5074]
MX29GL512GDT2@TSOP56 [DX1011]
MX29GL512GDXF@FBGA64 [DX5074]
MX29GL512GHT2@TSOP56 [DX1011]
MX29GL512GHXF@FBGA64 [DX5074]
MX29GL512GLT2@TSOP56 [DX1011]
MX29GL512GLXF@FBGA64 [DX5074]
MX29GL512GUT2@TSOP56 [DX1011]
MX29GL512GUXF@FBGA64 [DX5074]
MX29GL640EB@TSOP48 [DX1004]
MX29GL640EBXE@FBGA48 [DX5002]
MX29GL640EHT2@TSOP56 [DX1011]
MX29GL640EHXF@FBGA64 [DX5074]
MX29GL640ELT2@TSOP56 [DX1011]
MX29GL640ELXF@FBGA64 [DX5074]
MX29GL640ET@TSOP48 [DX1004]
MX29GL640ETXE@FBGA48 [DX5002]
MX29L1611 [DX0001]

MX29L1611@PSOP44 [DX1014]
MX29L1611@TSOP48 [DX1004]
MX29L3211@PSOP44 [DX1014]
MX29L3211@TSOP48 [DX1004]
MX29L8100B@TSOP48 [DX1004]
MX29L8100G [DX0001]
MX29L8100T@TSOP48 [DX1004]
MX29LA128DB@FBGA64 [DX5004]
MX29LA128DT@FBGA64 [DX5004]
MX29LA128MB@TSOP56 [DX1011]
MX29LA128MT@TSOP56 [DX1011]
MX29LA129DB@FBGA64 [DX5004]
MX29LA129DT@FBGA64 [DX5004]
MX29LA129MH@TSOP56 [DX1011]
MX29LA129ML@TSOP56 [DX1011]
MX29LA320DH@FBGA64 [DX5004]
MX29LA320DL@FBGA64 [DX5004]
MX29LA320MB@CFBGA48 [DX5002]
MX29LA320MB@TSOP48 [DX1004]
MX29LA320MT@CFBGA48 [DX5002]
MX29LA320MT@TSOP48 [DX1004]
MX29LA321DH@FBGA64 [DX5004]
MX29LA321DL@FBGA64 [DX5004]
MX29LA321MB@FBGA64 [DX5004]
MX29LA321MB@TSOP56 [DX1011]
MX29LA321MH@FBGA64 [DX5004]
MX29LA321MH@TSOP56 [DX1011]
MX29LA321ML@FBGA64 [DX5004]
MX29LA321ML@TSOP56 [DX1011]
MX29LA321MT@FBGA64 [DX5004]
MX29LA321MT@TSOP56 [DX1011]
MX29LA640EH@FBGA64 [DX5004]
MX29LA640EL@FBGA64 [DX5004]
MX29LA641DH@FBGA64 [DX5004]
MX29LA641DL@FBGA64 [DX5004]
MX29LV002CB@PLCC32 [DX2032]
MX29LV002CB@TSOP32 [DX1002]
MX29LV002CT@PLCC32 [DX2032]
MX29LV002CT@TSOP32 [DX1002]
MX29LV002NCB@PLCC32 [DX2032]
MX29LV002NCB@TSOP32 [DX1002]
MX29LV002NCT@PLCC32 [DX2032]
MX29LV002NCT@TSOP32 [DX1002]
MX29LV004B@PLCC32 [DX2032]
MX29LV004B@TSOP40 [DX1006]
MX29LV004CB@PLCC32 [DX2032]
MX29LV004CB@TSOP40 [DX1006]
MX29LV004CT@PLCC32 [DX2032]
MX29LV004CT@TSOP40 [DX1006]
MX29LV004T@PLCC32 [DX2032]
MX29LV004T@TSOP40 [DX1006]
MX29LV008B@TSOP40 [DX1006]
MX29LV008BB@TSOP40 [DX1006]
MX29LV008BT@TSOP40 [DX1006]
MX29LV008CB@TSOP40 [DX1006]
MX29LV008CT@TSOP40 [DX1006]
MX29LV008T@TSOP40 [DX1006]
MX29LV017AT@TSOP40 [DX1006]
MX29LV017AX@FBGA48 [DX5002]
MX29LV017BT@TSOP40 [DX1006]
MX29LV017BX@FBGA48 [DX5002]
MX29LV033AT@TSOP40 [DX1006]
MX29LV033M@TSOP40 [DX1006]
MX29LV033T@TSOP40 [DX1006]
MX29LV040@PLCC32 [DX2032]
MX29LV040@TSOP32 [DX1002]
MX29LV040C@PLCC32 [DX2032]
MX29LV040C@TSOP32 [DX1002]
MX29LV065BT@TSOP48 [DX1004]
MX29LV065BXB@FBGA63 [DX5041]
MX29LV065M@TSOP48 [DX1004]
MX29LV081@TSOP40 [DX1006]
MX29LV128DB@TSOP48 [DX1004]
MX29LV128DB@TSOP56 [DX1011]
MX29LV128DT@TSOP48 [DX1004]
MX29LV128DT@TSOP56 [DX1011]
MX29LV128MB@TSOP56 [DX1011]
MX29LV128MH@TSOP56 [DX1011]
MX29LV128ML@TSOP56 [DX1011]
MX29LV128MT@TSOP56 [DX1011]
MX29LV160AB(0.3)@CSP48 [DX5002]
MX29LV160AB(0.4)@CSP48 [DX5002]
MX29LV160AB@PSOP44 [DX1014]
MX29LV160AB@TSOP48 [DX1004]
MX29LV160AT(0.3)@CSP48 [DX5002]
MX29LV160AT(0.4)@CSP48 [DX5002]
MX29LV160AT@PSOP44 [DX1014]
MX29LV160AT@TSOP48 [DX1004]
MX29LV160B(0.3)@CSP48 [DX5002]
MX29LV160B(0.4)@CSP48 [DX5002]
MX29LV160B@PSOP44 [DX1014]
MX29LV160B@TSOP48 [DX1004]
MX29LV160BB(0.3)@CSP48 [DX5002]
MX29LV160BB(0.4)@CSP48 [DX5002]
MX29LV160BB@PSOP44 [DX1014]
MX29LV160BB@TSOP48 [DX1004]

MX29LV160BT(0.3)@CSP48 [DX5002]
MX29LV160BT(0.4)@CSP48 [DX5002]
MX29LV160BT@PSOP44 [DX1014]
MX29LV160BT@TSOP48 [DX1004]
MX29LV160CBM@PSOP44 [DX1014]
MX29LV160CBT@TSOP48 [DX1004]
MX29LV160CBXB(0.3)@CSP48 [DX5002]
MX29LV160CBXE(0.4)@CSP48 [DX5002]
MX29LV160CTM@PSOP44 [DX1014]
MX29LV160CTT@TSOP48 [DX1004]
MX29LV160CTXB(0.3)@CSP48 [DX5002]
MX29LV160CTXE(0.4)@CSP48 [DX5002]
MX29LV160DBGB@WFLGA48 [DX5037]
MX29LV160DBT@TSOP48 [DX1004]
MX29LV160DBXB@CSP48 [DX5002]
MX29LV160DBXE@CSP48 [DX5002]
MX29LV160DBXH@WFBGA48 [DX5037]
MX29LV160DTGB@WFLGA48 [DX5037]
MX29LV160DTT@TSOP48 [DX1004]
MX29LV160DTXB@CSP48 [DX5002]
MX29LV160DTXE@CSP48 [DX5002]
MX29LV160DTXH@WFBGA48 [DX5037]
MX29LV160T(0.3)@CSP48 [DX5002]
MX29LV160T(0.4)@CSP48 [DX5002]
MX29LV160T@PSOP44 [DX1014]
MX29LV160T@TSOP48 [DX1004]
MX29LV161DBGB@WFLGA48 [DX5037]
MX29LV161DBT@TSOP48 [DX1004]
MX29LV161DBXB@CSP48 [DX5002]
MX29LV161DBXH@WFBGA48 [DX5037]
MX29LV161DTGB@WFLGA48 [DX5037]
MX29LV161DTT@TSOP48 [DX1004]
MX29LV161DTXB@CSP48 [DX5002]
MX29LV161DTXH@WFBGA48 [DX5037]
MX29LV320ABT@TSOP48 [DX1004]
MX29LV320ABXB@CSP48 [DX5002]
MX29LV320ABXE@CSP48 [DX5002]
MX29LV320ATT@TSOP48 [DX1004]
MX29LV320ATXB@CSP48 [DX5002]
MX29LV320ATXE@CSP48 [DX5002]
MX29LV320BT@TSOP48 [DX1004]
MX29LV320BXB@CSP48 [DX5002]
MX29LV320BXE@CSP48 [DX5002]
MX29LV320CBT@TSOP48 [DX1004]
MX29LV320CBXB@CSP48 [DX5002]
MX29LV320CBXE@CSP48 [DX5002]
MX29LV320CTT@TSOP48 [DX1004]
MX29LV320CTXB@CSP48 [DX5002]
MX29LV320CTXE@CSP48 [DX5002]
MX29LV320DBT@TSOP48 [DX1004]
MX29LV320DBXB@CSP48 [DX5002]
MX29LV320DBXE@CSP48 [DX5002]
MX29LV320DTT@TSOP48 [DX1004]
MX29LV320DTXB@CSP48 [DX5002]
MX29LV320DTXE@CSP48 [DX5002]
MX29LV320EBB@CSP48 [DX5002]
MX29LV320EBE@CSP48 [DX5002]
MX29LV320EBT@TSOP48 [DX1004]
MX29LV320ETB@CSP48 [DX5002]
MX29LV320ETE@CSP48 [DX5002]
MX29LV320ETT@TSOP48 [DX1004]
MX29LV320MB@CFBGA48 [DX5002]
MX29LV320MB@PSOP44 [DX1014]
MX29LV320MB@TSOP48 [DX1004]
MX29LV320MH@TSOP56 [DX1011]
MX29LV320ML@TSOP56 [DX1011]
MX29LV320MT@CFBGA48 [DX5002]
MX29LV320MT@PSOP44 [DX1014]
MX29LV320MT@TSOP48 [DX1004]
MX29LV320TT@TSOP48 [DX1004]
MX29LV320TXB@CSP48 [DX5002]
MX29LV320TXE@CSP48 [DX5002]
MX29LV321DBT@TSOP48 [DX1004]
MX29LV321DBXB@CSP48 [DX5002]
MX29LV321DTT@TSOP48 [DX1004]
MX29LV321DTXB@FBGA48 [DX5002]
MX29LV400B@PSOP44 [DX1014]
MX29LV400B@TSOP48 [DX1004]
MX29LV400BX(0.3)@CSP48 [DX5002]
MX29LV400BX(0.4)@CSP48 [DX5002]
MX29LV400CBM@PSOP44 [DX1014]
MX29LV400CBT@TSOP48 [DX1004]
MX29LV400CBXB(0.3)@CSP48 [DX5002]
MX29LV400CBXE(0.4)@CSP48 [DX5002]
MX29LV400CTM@PSOP44 [DX1014]
MX29LV400CTT@TSOP48 [DX1004]
MX29LV400CTXB(0.3)@CSP48 [DX5002]
MX29LV400CTXE(0.4)@CSP48 [DX5002]

MX29LV400T@PSOP44 [DX1014]
MX29LV400T@TSOP48 [DX1004]
MX29LV400TX(0.3)@CSP48 [DX5002]
MX29LV400TX(0.4)@CSP48 [DX5002]
MX29LV640BBT@TSOP48 [DX1004]
MX29LV640BBXB@FBGA63 [DX5041]
MX29LV640BT@TSOP48 [DX1004]
MX29LV640BTT@TSOP48 [DX1004]
MX29LV640BTXB@FBGA63 [DX5041]
MX29LV640BUT@TSOP48 [DX1004]
MX29LV640BUXB@FBGA63 [DX5041]
MX29LV640BXB@FBGA63 [DX5041]
MX29LV640BXC@FBGA64 [DX5004]
MX29LV640DBM@PSOP44 [DX1014]
MX29LV640DBT@TSOP48 [DX1004]
MX29LV640DBX@FBGA48 [DX5002]
MX29LV640DTM@PSOP44 [DX1014]
MX29LV640DTT@TSOP48 [DX1004]
MX29LV640DTX@FBGA48 [DX5002]
MX29LV640EBT@TSOP48 [DX1004]
MX29LV640EBX@FBGA48 [DX5002]
MX29LV640ETT@TSOP48 [DX1004]
MX29LV640ETX@FBGA48 [DX5002]
MX29LV640MB@FBGA63 [DX5041]
MX29LV640MB@TSOP48 [DX1004]
MX29LV640MH@FBGA64 [DX5004]
MX29LV640MH@TSOP56 [DX1011]
MX29LV640ML@FBGA64 [DX5004]
MX29LV640ML@TSOP56 [DX1011]
MX29LV640MT@FBGA63 [DX5041]
MX29LV640MT@TSOP48 [DX1004]
MX29LV640MU@FBGA63 [DX5041]
MX29LV640TT@TSOP48 [DX1004]
MX29LV640TXB@FBGA63 [DX5041]
MX29LV640TXC@FBGA64 [DX5004]
MX29LV640UT@TSOP48 [DX1004]
MX29LV640UXB@FBGA63 [DX5041]
MX29LV640UXC@FBGA64 [DX5004]
MX29LV641MH@TSOP48 [DX1004]
MX29LV641ML@TSOP48 [DX1004]
MX29LV800AB(0.3)@CSP48 [DX5002]
MX29LV800AB(0.4)@CSP48 [DX5002]
MX29LV800AB@PSOP44 [DX1014]
MX29LV800AB@TSOP48 [DX1004]
MX29LV800AT(0.3)@CSP48 [DX5002]
MX29LV800AT(0.4)@CSP48 [DX5002]
MX29LV800AT@PSOP44 [DX1014]
MX29LV800AT@TSOP48 [DX1004]
MX29LV800B(0.3)@CSP48 [DX5002]
MX29LV800B(0.4)@CSP48 [DX5002]
MX29LV800B@PSOP44 [DX1014]
MX29LV800B@TSOP48 [DX1004]
MX29LV800CBM@PSOP44 [DX1014]
MX29LV800CBT@TSOP48 [DX1004]
MX29LV800CBXB(0.3)@CSP48 [DX5002]
MX29LV800CBXE(0.4)@CSP48 [DX5002]
MX29LV800CTM@PSOP44 [DX1014]
MX29LV800CTT@TSOP48 [DX1004]
MX29LV800CTXB(0.3)@CSP48 [DX5002]
MX29LV800CTXE(0.4)@CSP48 [DX5002]
MX29LV800T(0.3)@CSP48 [DX5002]
MX29LV800T(0.4)@CSP48 [DX5002]
MX29LV800T@PSOP44 [DX1014]
MX29LV800T@TSOP48 [DX1004]
MX29LW160BT@TSOP48 [DX1004]
MX29LW160BXA(0.75)@CSP48 [DX50UN]
MX29LW160BXB(0.80)@CSP48 [DX5022]
MX29LW160TT@TSOP48 [DX1004]
MX29LW160TXA(0.75)@CSP48 [DX50UN]
MX29LW160TXB(0.80)@CSP48 [DX5005]
MX29LW161BT@TSOP48 [DX1004]
MX29LW161BXA(0.75)@CSP48 [DX50UN]
MX29LW161BXB(0.80)@CSP48 [DX5022]
MX29LW161TT@TSOP48 [DX1004]
MX29LW161TXA(0.75)@CSP48 [DX50UN]
MX29LW161TXB(0.80)@CSP48 [DX5022]
MX29LW320BT@TSOP48 [DX1004]
MX29LW320BXA(0.75)@CSP48 [DX50UN]

MX29LW320BXB(0.80)@CSP48 [DX5005]
MX29LW320TT@TSOP48 [DX1004]
MX29LW320TXA(0.75)@CSP48 [DX50UN]
MX29LW320TXB(0.80)@CSP48 [DX5005]
MX29LW321BT@TSOP48 [DX1004]
MX29LW321BXA(0.75)@CSP48 [DX50UN]
MX29LW321BXB(0.80)@CSP48 [DX5005]
MX29LW321TT@TSOP48 [DX1004]
MX29LW321TXA(0.75)@CSP48 [DX50UN]
MX29LW321TXB(0.80)@CSP48 [DX5005]
MX29NS128EXJ1@FBGA56 [DX5094]
MX29NS320EXJ1@FBGA56 [DX5094]
MX29NS640EXJ1@FBGA56 [DX5094]
MX29SL402CBGB@WFLGA48 [DX5037]
MX29SL402CBT@TSOP48 [DX1004]
MX29SL402CBXB@CSP48 [DX5002]
MX29SL402CBXE@CSP48 [DX5002]
MX29SL402CBXH@WFBGA48 [DX5037]
MX29SL402CTGB@WFLGA48 [DX5037]
MX29SL402CTT@TSOP48 [DX1004]
MX29SL402CTXB@CSP48 [DX5002]
MX29SL402CTXE@CSP48 [DX5002]
MX29SL402CTXH@WFBGA48 [DX5037]
MX29SL800CB@TSOP48 [DX1004]
MX29SL800CBXB(0.30)@CSP48 [DX5002]
MX29SL800CBXE(0.40)@CSP48 [DX5002]
MX29SL800CBXH(0.30)@CSP48 [DX5038]
MX29SL800CT@TSOP48 [DX1004]
MX29SL800CTXB(0.30)@CSP48 [DX5002]
MX29SL800CTXE(0.40)@CSP48 [DX5002]
MX29SL800CTXH(0.30)@CSP48 [DX5038]
MX29SL802CBGB@WFLGA48 [DX5037]
MX29SL802CBT@TSOP48 [DX1004]
MX29SL802CBXB@CSP48 [DX5002]
MX29SL802CBXE@CSP48 [DX5002]
MX29SL802CBXH@WFBGA48 [DX5037]
MX29SL802CTGB@WFLGA48 [DX5037]
MX29SL802CTT@TSOP48 [DX1004]
MX29SL802CTXB@CSP48 [DX5002]
MX29SL802CTXE@CSP48 [DX5002]
MX29SL802CTXH@WFBGA48 [DX5037]
MX30LF2G18AC@TSOP48 [DX1004-1]
MX30LF4G18AC@TSOP48 [DX1004-1]
MX30LF4GE8AC@TSOP48 [DX1004-1]
MX30UF4G28AB@FBGA63 [DX5046]
MX66L51235F@SOP16 [DX1033#1]
MX66L51235F@TFBGA24 [DX5157]
MX66L51235F@WSON8 [DX4006#1]
MX68GA1G0FHXF@FBGA64 [DX5074]
MX68GA1G0FLXF@FBGA64 [DX5074]
MX68GL1G0FDT2@TSOP56 [DX1011]
MX68GL1G0FDXF@FBGA64 [DX5074]
MX68GL1G0FHT2@TSOP56 [DX1011]
MX68GL1G0FHXF@FBGA64 [DX5074]
MX68GL1G0FLT2@TSOP56 [DX1011]
MX68GL1G0FLXF@FBGA64 [DX5074]
MX68GL1G0FUT2@TSOP56 [DX1011]
MX68GL1G0FUXF@FBGA64 [DX5074]
MX68GL1G0GDT2@TSOP56 [DX1011]
MX68GL1G0GDXF@FBGA64 [DX5074]
MX68GL1G0GHT2@TSOP56 [DX1011]
MX68GL1G0GHXF@FBGA64 [DX5074]
MX68GL1G0GLT2@TSOP56 [DX1011]
MX68GL1G0GLXF@FBGA64 [DX5074]
MX68GL1G0GUT2@TSOP56 [DX1011]
MX68GL1G0GUXF@FBGA64 [DX5074]
MX69F1602C3BX@FBGA72 [DX5001]
MX69F1602C3TX@FBGA72 [DX5001]
MX69F1604C3BX@FBGA72 [DX5001]
MX69F1604C3TX@FBGA72 [DX5001]
MX69F3204C3BX@FBGA72 [DX5026]
MX69F3204C3TX@FBGA72 [DX5026]
MX69GL127EAXGW@FBGA56 [DX5045]
MX69GL127EBXGW@FBGA56 [DX5045]
MX69GL127ECXGW@FBGA56 [DX5045]
MX69GL128EAXGW@FBGA64 [DX5001]
MX69GL128EBXGW@FBGA64 [DX5001]
MX69GL128ECXGW@FBGA64 [DX5001]
MX69GL638EAXGI@FBGA56 [DX5045]

MX69GL638EJXGI@FBGA56 [DX5045]
MX69GL640EAXGI@FBGA56 [DX5045]
MX69GL640EAXGW@FBGA56 [DX5045]
MX69GL640EBXGW@FBGA56 [DX5045]
MX69GL640ECXGW@FBGA56 [DX5045]
MX69GL640EJXGI@FBGA56 [DX5045]
MX69GL642EAXGI@FBGA56 [DX5045]
MX69GL642EJXGI@FBGA56 [DX5045]
MX69LW162BXB@CSP69 [DX5001]
MX69LW162TXB@CSP69 [DX5001]
MX69LW164BXB@CSP69 [DX5001]
MX69LW164TXB@CSP69 [DX5001]
MX69LW322BXB@CSP69 [DX5001]
MX69LW322TXB@CSP69 [DX5001]
MX69LW324BXB@CSP69 [DX5001]
MX69LW324TXB@CSP69 [DX5001]
MX69N28E32AXJW@FBGA56 [DX5094]
MX69N28E32BXJW@FBGA56 [DX5094]
MX69N28E32FXJW@FBGA56 [DX5094]
MX69N28E64AXJW@FBGA56 [DX5094]
MX69N28E64FXJW@FBGA56 [DX5094]
MX69N64E32AXJW@FBGA56 [DX5094]
MX69N64E32BXJW@FBGA56 [DX5094]
MX69N64E32FXJW@FBGA56 [DX5094]
MX69V28F32BBXJW@FBGA56 [DX5094]
MX69V28F64BBXJW@FBGA56 [DX5094]
MX69V28F64BBXLW@FBGA56 [DX5094]
MX69V28F64BMXJW@FBGA56 [DX5094]
MX69V28F64MBXLW@FBGA56 [DX5094]

MICROCONTROLLER

MX10E8050I [DX0001]
MX10E8050I@PLCC44 [DX2044]
MX10E8050I@TQFP44 [DX3003]
MX10EXAQ@PLCC44 [DX2044]
MX10EXAU@TQFP44 [DX3003]
MX10F201FC@TQFP100 [DX3023]
MX10F202FC@TQFP100 [DX3023]
MX10FLCD [DX0001]
MX10FMAXD [DX0001]
MX10FMAXD@PLCC44 [DX2044]
MX10FMAXD@TQFP44 [DX3002]

MAGNACHIP

MICROCONTROLLER

GMS34004TK [DX0001]
GMS34004TM [DX0001]
GMS34004TW [DX0001]
GMS34112TK [DX0001]
GMS34112TK@SOIC20 [DX1033]
GMS34112TK@SSOP20 [DX1026]
GMS34140TK [DX0001]
GMS34140TK@SOIC24 [DX1033]
GMS81504AT [DX0032]
GMS81504T [DX0032]
GMS81604T [DX0001]
GMS81604T@PLCC44 [DX2044]
GMS81604T@SDIP42 [DX0042]
GMS81608T [DX0001]
GMS81608T@PLCC44 [DX2044]
GMS81608T@SDIP42 [DX0042]
GMS87C1102 [DX0001]
GMS87C1102@SOP16 [DX1033]
GMS87C1202 [DX0001]
GMS87C1202@SOP20 [DX1033]
GMS87C1404 [DX0001]
GMS87C1404@SOP28 [DX1033]
GMS87C1408 [DX0001]
GMS87C1408@SOP28 [DX1033]
GMS87C2020@LQFP64 [DX3011]
GMS87C2020@MQFP64 [DX3015]
GMS87C2020@SDIP64 [DX0064]
GMS87C5108@PQFP80 [DX3019]
GMS87C7008@LQFP64 [DX3011]
GMS87C7008@MQFP64 [DX3015]
GMS87C7008@SDIP64 [DX0064]
GMS87C7016@LQFP64 [DX3011]
GMS87C7016@MQFP64 [DX3015]
GMS87C7016@SDIP64 [DX0064]

GMS97C1051 [DX0001]
GMS97C1051@SOIC20 [DX1033]
GMS97C2051 [DX0001]
GMS97C2051@SOIC20 [DX1033]
GMS97C51 [DX0001]
GMS97C51@PLCC44 [DX2044]
GMS97C51@TQFP44 [DX3002]
GMS97C51H [DX0001]
GMS97C51H@PLCC44 [DX2044]
GMS97C51H@TQFP44 [DX3002]
GMS97C52 [DX0001]
GMS97C52@PLCC44 [DX2044]
GMS97C52@TQFP44 [DX3002]
GMS97C52H [DX0001]
GMS97C52H@PLCC44 [DX2044]
GMS97C52H@TQFP44 [DX3002]
GMS97C54 [DX0001]
GMS97C54@PLCC44 [DX2044]
GMS97C54@TQFP44 [DX3002]
GMS97C54H [DX0001]
GMS97C54H@PLCC44 [DX2044]
GMS97C54H@TQFP44 [DX3002]
GMS97C56 [DX0001]
GMS97C56@PLCC44 [DX2044]
GMS97C56@TQFP44 [DX3002]
GMS97C56H [DX0001]
GMS97C56H@PLCC44 [DX2044]
GMS97C56H@TQFP44 [DX3002]
GMS97C58 [DX0001]
GMS97C58@PLCC44 [DX2044]
GMS97C58@TQFP44 [DX3002]
GMS97C58H [DX0001]
GMS97C58H@PLCC44 [DX2044]
GMS97C58H@TQFP44 [DX3002]
GMS97L1051 [DX0001]
GMS97L1051@SOIC20 [DX1033]
GMS97L2051 [DX0001]
GMS97L2051@SOIC20 [DX1033]
GMS97L51 [DX0001]
GMS97L51@PLCC44 [DX2044]
GMS97L51@TQFP44 [DX3002]
GMS97L52 [DX0001]
GMS97L52@PLCC44 [DX2044]
GMS97L52@TQFP44 [DX3002]
GMS97L54 [DX0001]
GMS97L54@PLCC44 [DX2044]
GMS97L54@TQFP44 [DX3002]
GMS97L56 [DX0001]
GMS97L56@PLCC44 [DX2044]
GMS97L56@TQFP44 [DX3002]
GMS97L58 [DX0001]
GMS97L58@PLCC44 [DX2044]
GMS97L58@TQFP44 [DX3002]
HMS87C1404B [DX0001]
HMS87C1404B@SDIP28 [DX0032]
HMS87C1404B@SOIC28 [DX1033]
HMS87C1408B [DX0001]
HMS87C1408B@SDIP28 [DX0032]
HMS87C1408B@SOIC28 [DX1033]
HMS87C1416B [DX0001]
HMS87C1416B@SDIP28 [DX0032]
HMS87C1416B@SOIC28 [DX1033]
HMS87C1508B [DX0001]
HMS87C1516B [DX0001]
HMS87C1608B [DX0001]
HMS87C1616B [DX0001]
HMS87C1708B@SDIP42 [DX0042]
HMS87C1716B@SDIP42 [DX0042]
HMS87C1808B@TQFP44 [DX3002]
HMS87C1816B@TQFP44 [DX3002]
HMS87C5216 [DX0001]
HMS87C5216@PLCC44 [DX2044]
HMS87C5216@SOIC28 [DX1033]
HMS87C5216@TQFP44 [DX3002]
MC80F0504 [DX0001]
MC80F0504@SOP16 [DX1036]
MC80F0504@SSOP16 [DX1026]
MC80F0504[153mil]@SOP16 [DX1030]
MC80F0604 [DX0001]
MC80F0604@SOP20 [DX1036]
MC80F0604@SSOP20 [DX1026]
MC80F0704 [DX0001]
MC80F0704@QFN28 [DX0001]
MC80F0704@SOP28 [DX1036]
MC80F0708 [DX0001]
MC80F0708@QFN28 [DX0001]
MC80F0708@SOP28 [DX1036]
MC80F0804@SDIP32 [DX0032]
MC80F0804@SOP32 [DX1069]
MC80F0808@SDIP32 [DX0032]
MC80F0808@SOP32 [DX1069]

MAXCOM

E(E)PROM/FRAM/NVRAM

MAX24A02 [DX0001]
MAX24A02@SOP8 [DX1045]
MAX24A02@TSSOP8 [DX1059]
MAX24A04 [DX0001]
MAX24A04@SOP8 [DX1045]
MAX24A04@TSSOP8 [DX1059]
MAX24A08 [DX0001]
MAX24A08@SOP8 [DX1045]
MAX24A08@TSSOP8 [DX1059]
MAX24A16 [DX0001]
MAX24A16@SOP8 [DX1045]
MAX24A16@TSSOP8 [DX1059]

MAXIM

E(E)PROM/FRAM/NVRAM

DS1220AB [DX0001]
DS1220AD [DX0001]
DS1220Y [DX0001]
DS1225AB [DX0001]
DS1225AD [DX0001]
DS1225D [DX0001]
DS1225E [DX0001]
DS1225Y [DX0001]
DS1230AB [DX0001]
DS1230W [DX0001]
DS1230Y [DX0001]
DS1235AB [DX0001]
DS1235Y [DX0001]
DS1243Y [DX0001]
DS1244 [DX0001]
DS1244P [DX2068]
DS1244Y [DX0001]
DS1244YP [DX2068]
DS1245AB [DX0001]
DS1245EE [DX0001]
DS1245P [DX2068]
DS1245W [DX0001]
DS1245Y [DX0001]
DS1248P [DX2068]
DS1248W [DX0001]
DS1248Y [DX0001]
DS1249AB [DX0001]
DS1249W [DX0001]
DS1249Y [DX0001]
DS1250AB [DX0001]
DS1250W [DX0001]
DS1250Y [DX0001]
DS1251AB [DX0001]
DS1251W [DX0001]
DS1251Y [DX0001]
DS1256P [DX2068]
DS1256W [DX0001]
DS1256Y [DX0001]
DS1258AB [DX0001]
DS1258W [DX0001]
DS1258Y [DX0001]
DS1265AB [DX0001]
DS1265W [DX0001]
DS1265Y [DX0001]
DS1270AB [DX0001]
DS1270W [DX0001]
DS1270Y [DX0001]
DS1284 [DX0001]
DS1284N [DX0001]
DS1284Q@PLCC28 [DX2028]
DS1284QN@PLCC28 [DX2028]
DS1286 [DX0001]
DS1286I [DX0001]
DS1287 [DX0001]
DS1287A [DX0001]
DS12887 [DX0001]
DS12887A [DX0001]
DS12C887 [DX0001]
DS12C887A [DX0001]
DS1386(32K) [DX0001]
DS1386(8K) [DX0001]
DS1485 [DX0001]
DS1485@SOIC28 [DX1035]
DS1488 [DX0001]

DS1501 [DX0001]
DS1511 [DX0001]
DS1553 [DX0001]
DS1553P [DX2068]
DS1553W [DX0001]
DS1553WP [DX2068]
DS1554 [DX0001]
DS1554W [DX0001]
DS1556 [DX0001]
DS1642 [DX0001]
DS1643 [DX0001]
DS1644 [DX0001]
DS1644P [DX2068]
DS1644PS [DX2068]
DS1645AB [DX0001]
DS1645EE [DX0001]
DS1645Y [DX0001]
DS1646 [DX0001]
DS1646P [DX2068]
DS1647 [DX0001]
DS1647LPM [DX2068]
DS1650AB [DX0001]
DS1650Y [DX0001]
DS1685-3 [DX0001]
DS1685-3@SOP24 [DX1033]
DS1685-5 [DX0001]
DS1685-5@SOP24 [DX1033]
DS1687-3 [DX0001]
DS1687-5 [DX0001]
DS17287-3 [DX0001]
DS17287-5 [DX0001]
DS1742 [DX0001]
DS1742W [DX0001]
DS1743 [DX0001]
DS1743P [DX2068]
DS1743W [DX0001]
DS1743WP [DX2068]
DS1744 [DX0001]
DS1744P [DX2068]
DS1744W [DX0001]
DS1744WP [DX2068]
DS1746 [DX0001]
DS1746P [DX2068]
DS1747 [DX0001]
DS1747P [DX2068]
DS1747PS [DX2068]
DS1747W [DX0001]
DS1747WP [DX2068]
DS1747WPS [DX2068]
DS17487-3 [DX0001]
DS17487-5 [DX0001]
DS17887-3 [DX0001]
DS17887-5 [DX0001]
DS2430A@TO-92 [DX0001]
DS2430AP@TSOC6 [DX1066]
DS2431@TDFN6 [DX4000]
DS2431@TO-92 [DX0001]
DS2431P@TSOC6 [DX1066]
DS2432P@TSOC6 [DX1066]
DS2433@PR-35 [DX0001]
DS2433S(3.9)@SOIC8 [DX1045]
DS2433S(5.5)@SOIC8 [DX1044]
DS2502 [DX0001]
DS2502P@TSOC6 [DX1066]
DS2502S@SOIC8 [DX1045]
DS2502UNW [DX0001]
DS2502UNW@SOIC8 [DX1045]
DS2502UNW@SOT-23 [DX1041]
DS2502UNW@TSOC6 [DX1066]
DS2505 [DX0001]
DS2505S@TSOC6 [DX1066]
DS2506 [DX0001]
DS2506S@SOIC8 [DX1045]
DS4510@uSOP10 [DX1016]
DS4520@TSSOP16 [DX1000]
DS4550@TSSOP20 [DX1000]
MAX9668@QFN20 [DX4025]
MAX9669@QFN28 [DX4013]
MAX9674@QFN28 [DX4013]
MAX9674@QFN28(LD) [DX4013]

MICROCONTROLLER

71M6513H-IGT [DX3021-7]
71M6513H-IGTR [DX3021-7]
71M6513-IGT [DX3021-7]
71M6513-IGTR [DX3021-7]
71M6521BE-IGT [DX3011-13]
71M6521BE-IM [DX4026-1]
71M6521DE-IGT [DX3011-13]
71M6521DE-IM [DX4026-1]

71M6521FE-IGT [DX3011-13]
71M6521FE-IM [DX4026-1]
BQ2022ADBZR [DX1041]
BQ2022ALPR [DX0001]
BQ2022DBZR [DX1041]
BQ2022LPR [DX0001]
DS2760@TSSOP16 [DX1001]
DS5000 [8K] [DX0001]
DS5000 [32K] [DX0001]
DS5000T [8K] [DX0001]
DS5000T [32K] [DX0001]
DS87C520 [DX0001]
DS87C520@PLCC44 [DX2044]
DS87C520@TQFP44 [DX3003]
DS87C530@PLCC52 [DX2052]
DS87C550@PLCC68 [DX2068]
DS89C420(rev.A) [DX0001]
DS89C420(rev.A)@PLCC44 [DX2044]
DS89C420(rev.A)@TQFP44 [DX3003]
MAX6889@QFN32 [DX4015]
MAX7651CCB@TQFP64 [DX3011]
MAX7651ECB@TQFP64 [DX3011]
MAX7652CCB@TQFP64 [DX3011]
MAX7652ECB@TQFP64 [DX3011]
MAX9696@QFN24 [DX4012]
MAX9696@QFN24(left down) [DX4012]
ZGP323HAH2004C@SSOP20 [DX1026]
ZGP323HAH2004G@SSOP20 [DX1026]
ZGP323HAH2008C@SSOP20 [DX1026]
ZGP323HAH2008G@SSOP20 [DX1026]
ZGP323HAH2016C@SSOP20 [DX1026]
ZGP323HAH2016G@SSOP20 [DX1026]
ZGP323HAH2032C@SSOP20 [DX1026]
ZGP323HAH2032G@SSOP20 [DX1026]
ZGP323HAH2804C@SSOP28 [DX1026]
ZGP323HAH2804G@SSOP28 [DX1026]
ZGP323HAH2808C@SSOP28 [DX1026]
ZGP323HAH2808G@SSOP28 [DX1026]
ZGP323HAH2816C@SSOP28 [DX1026]
ZGP323HAH2816G@SSOP28 [DX1026]
ZGP323HAH2832C@SSOP28 [DX1026]
ZGP323HAH2832G@SSOP28 [DX1026]
ZGP323HAH4804C@SSOP48 [DX1028]
ZGP323HAH4804G@SSOP48 [DX1028]
ZGP323HAH4808C@SSOP48 [DX1028]
ZGP323HAH4808G@SSOP48 [DX1028]
ZGP323HAH4816C@SSOP48 [DX1028]
ZGP323HAH4816G@SSOP48 [DX1028]
ZGP323HAH4832C@SSOP48 [DX1028]
ZGP323HAH4832G@SSOP48 [DX1028]
ZGP323HAP2004C [DX0001]
ZGP323HAP2004G [DX0001]
ZGP323HAP2008C [DX0001]
ZGP323HAP2008G [DX0001]
ZGP323HAP2016C [DX0001]
ZGP323HAP2016G [DX0001]
ZGP323HAP2032C [DX0001]
ZGP323HAP2032G [DX0001]
ZGP323HAP2804C [DX0001]
ZGP323HAP2804G [DX0001]
ZGP323HAP2808C [DX0001]
ZGP323HAP2808G [DX0001]
ZGP323HAP2816C [DX0001]
ZGP323HAP2816G [DX0001]
ZGP323HAP2832C [DX0001]
ZGP323HAP2832G [DX0001]
ZGP323HAP4004C [DX0001]
ZGP323HAP4004G [DX0001]
ZGP323HAP4008C [DX0001]
ZGP323HAP4008G [DX0001]
ZGP323HAP4016C [DX0001]
ZGP323HAP4016G [DX0001]
ZGP323HAP4032C [DX0001]
ZGP323HAP4032G [DX0001]
ZGP323HAS2004C@SOIC20 [DX1033]
ZGP323HAS2004G@SOIC20 [DX1033]
ZGP323HAS2008C@SOIC20 [DX1033]
ZGP323HAS2008G@SOIC20 [DX1033]
ZGP323HAS2016C@SOIC20 [DX1033]
ZGP323HAS2016G@SOIC20 [DX1033]
ZGP323HAS2032C@SOIC20 [DX1033]
ZGP323HAS2032G@SOIC20 [DX1033]
ZGP323HAS2804C@SOIC28 [DX1033]
ZGP323HAS2804G@SOIC28 [DX1033]
ZGP323HAS2808C@SOIC28 [DX1033]
ZGP323HAS2808G@SOIC28 [DX1033]
ZGP323HAS2816C@SOIC28 [DX1033]
ZGP323HAS2816G@SOIC28 [DX1033]
ZGP323HAS2832C@SOIC28 [DX1033]
ZGP323HAS2832G@SOIC28 [DX1033]
ZGP323HEH2004C@SSOP20 [DX1026]
ZGP323HEH2004G@SSOP20 [DX1026]
ZGP323HEH2008C@SSOP20 [DX1026]
ZGP323HEH2008G@SSOP20 [DX1026]

ZGP323HEH2016C@SSOP20 [DX1026]
ZGP323HEH2032C@SSOP20 [DX1026]
ZGP323HEH2804C@SSOP28 [DX1026]
ZGP323HEH2808C@SSOP28 [DX1026]
ZGP323HEH2816C@SSOP28 [DX1026]
ZGP323HEH2832C@SSOP28 [DX1026]
ZGP323HEH4804C@SSOP48 [DX1028]
ZGP323HEH4808C@SSOP48 [DX1028]
ZGP323HEH4816C@SSOP48 [DX1028]
ZGP323HEH4832C@SSOP48 [DX1028]
ZGP323HEP2004C [DX0001]
ZGP323HEP2008C [DX0001]
ZGP323HEP2016C [DX0001]
ZGP323HEP2032C [DX0001]
ZGP323HEP2804C [DX0001]
ZGP323HEP2808C [DX0001]
ZGP323HEP2816C [DX0001]
ZGP323HEP2832C [DX0001]
ZGP323HEP4004C [DX0001]
ZGP323HEP4008C [DX0001]
ZGP323HEP4016C [DX0001]
ZGP323HEP4032C [DX0001]
ZGP323HES2004C@SOIC20 [DX1033]
ZGP323HES2008C@SOIC20 [DX1033]
ZGP323HES2016C@SOIC20 [DX1033]
ZGP323HES2032C@SOIC20 [DX1033]
ZGP323HES2804C@SOIC28 [DX1033]
ZGP323HES2808C@SOIC28 [DX1033]
ZGP323HES2816C@SOIC28 [DX1033]
ZGP323HES2832C@SOIC28 [DX1033]
ZGP323HSH2004C@SSOP20 [DX1026]
ZGP323HSH2008C@SSOP20 [DX1026]
ZGP323HSH2016C@SSOP20 [DX1026]
ZGP323HSH2032C@SSOP20 [DX1026]
ZGP323HSH2804C@SSOP28 [DX1026]
ZGP323HSH2808C@SSOP28 [DX1026]
ZGP323HSH2816C@SSOP28 [DX1026]
ZGP323HSH2832C@SSOP28 [DX1026]
ZGP323HSH4804C@SSOP48 [DX1028]
ZGP323HSH4808C@SSOP48 [DX1028]
ZGP323HSH4816C@SSOP48 [DX1028]
ZGP323HSH4832C@SSOP48 [DX1028]
ZGP323HSP2004C [DX0001]
ZGP323HSP2008C [DX0001]
ZGP323HSP2016C [DX0001]
ZGP323HSP2032C [DX0001]
ZGP323HSP2804C [DX0001]
ZGP323HSP2808C [DX0001]

ZGP323HEH2016G@SSOP20 [DX1026]
ZGP323HEH2032G@SSOP20 [DX1026]
ZGP323HEH2804G@SSOP28 [DX1026]
ZGP323HEH2808G@SSOP28 [DX1026]
ZGP323HEH2816G@SSOP28 [DX1026]
ZGP323HEH2832G@SSOP28 [DX1026]
ZGP323HEH4804G@SSOP48 [DX1028]
ZGP323HEH4808G@SSOP48 [DX1028]
ZGP323HEH4816G@SSOP48 [DX1028]
ZGP323HEH4832G@SSOP48 [DX1028]
ZGP323HEP2004G [DX0001]
ZGP323HEP2008G [DX0001]
ZGP323HEP2016G [DX0001]
ZGP323HEP2032G [DX0001]
ZGP323HEP2804G [DX0001]
ZGP323HEP2808G [DX0001]
ZGP323HEP2816G [DX0001]
ZGP323HEP2832G [DX0001]
ZGP323HEP4004G [DX0001]
ZGP323HEP4008G [DX0001]
ZGP323HEP4016G [DX0001]
ZGP323HEP4032G [DX0001]
ZGP323HES2004G@SOIC20 [DX1033]
ZGP323HES2008G@SOIC20 [DX1033]
ZGP323HES2016G@SOIC20 [DX1033]
ZGP323HES2032G@SOIC20 [DX1033]
ZGP323HES2804G@SOIC28 [DX1033]
ZGP323HES2808G@SOIC28 [DX1033]
ZGP323HES2816G@SOIC28 [DX1033]
ZGP323HES2832G@SOIC28 [DX1033]
ZGP323HSH2004G@SSOP20 [DX1026]
ZGP323HSH2008G@SSOP20 [DX1026]
ZGP323HSH2016G@SSOP20 [DX1026]
ZGP323HSH2032G@SSOP20 [DX1026]
ZGP323HSH2804G@SSOP28 [DX1026]
ZGP323HSH2808G@SSOP28 [DX1026]
ZGP323HSH2816G@SSOP28 [DX1026]
ZGP323HSH2832G@SSOP28 [DX1026]
ZGP323HSH4804G@SSOP48 [DX1028]
ZGP323HSH4808G@SSOP48 [DX1028]
ZGP323HSH4816G@SSOP48 [DX1028]
ZGP323HSH4832G@SSOP48 [DX1028]
ZGP323HSP2004G [DX0001]
ZGP323HSP2008G [DX0001]
ZGP323HSP2016G [DX0001]
ZGP323HSP2032G [DX0001]
ZGP323HSP2804G [DX0001]
ZGP323HSP2808G [DX0001]

ZGP323HSP2816C [DX0001]	ZGP323HSP2816G [DX0001]
ZGP323HSP2832C [DX0001]	ZGP323HSP2832G [DX0001]
ZGP323HSP4004C [DX0001]	ZGP323HSP4004G [DX0001]
ZGP323HSP4008C [DX0001]	ZGP323HSP4008G [DX0001]
ZGP323HSP4016C [DX0001]	ZGP323HSP4016G [DX0001]
ZGP323HSP4032C [DX0001]	ZGP323HSP4032G [DX0001]
ZGP323HSS2004C@SOIC20 [DX1033]	ZGP323HSS2004G@SOIC20 [DX1033]
ZGP323HSS2008C@SOIC20 [DX1033]	ZGP323HSS2008G@SOIC20 [DX1033]
ZGP323HSS2016C@SOIC20 [DX1033]	ZGP323HSS2016G@SOIC20 [DX1033]
ZGP323HSS2032C@SOIC20 [DX1033]	ZGP323HSS2032G@SOIC20 [DX1033]
ZGP323HSS2804C@SOIC28 [DX1033]	ZGP323HSS2804G@SOIC28 [DX1033]
ZGP323HSS2808C@SOIC28 [DX1033]	ZGP323HSS2808G@SOIC28 [DX1033]
ZGP323HSS2816C@SOIC28 [DX1033]	ZGP323HSS2816G@SOIC28 [DX1033]
ZGP323HSS2832C@SOIC28 [DX1033]	ZGP323HSS2832G@SOIC28 [DX1033]
ZGP323LAH2004C@SSOP20 [DX1026]	ZGP323LAH2004G@SSOP20 [DX1026]
ZGP323LAH2008C@SSOP20 [DX1026]	ZGP323LAH2008G@SSOP20 [DX1026]
ZGP323LAH2016C@SSOP20 [DX1026]	ZGP323LAH2016G@SSOP20 [DX1026]
ZGP323LAH2032C@SSOP20 [DX1026]	ZGP323LAH2032G@SSOP20 [DX1026]
ZGP323LAH2804C@SSOP28 [DX1026]	ZGP323LAH2804G@SSOP28 [DX1026]
ZGP323LAH2808C@SSOP28 [DX1026]	ZGP323LAH2808G@SSOP28 [DX1026]
ZGP323LAH2816C@SSOP28 [DX1026]	ZGP323LAH2816G@SSOP28 [DX1026]
ZGP323LAH2832C@SSOP28 [DX1026]	ZGP323LAH2832G@SSOP28 [DX1026]
ZGP323LAH4804C@SSOP48 [DX1028]	ZGP323LAH4804G@SSOP48 [DX1028]
ZGP323LAH4808C@SSOP48 [DX1028]	ZGP323LAH4808G@SSOP48 [DX1028]
ZGP323LAH4816C@SSOP48 [DX1028]	ZGP323LAH4816G@SSOP48 [DX1028]
ZGP323LAH4832C@SSOP48 [DX1028]	ZGP323LAH4832G@SSOP48 [DX1028]
ZGP323LAP2004C [DX0001]	ZGP323LAP2004G [DX0001]
ZGP323LAP2008C [DX0001]	ZGP323LAP2008G [DX0001]
ZGP323LAP2016C [DX0001]	ZGP323LAP2016G [DX0001]
ZGP323LAP2032C [DX0001]	ZGP323LAP2032G [DX0001]
ZGP323LAP2804C [DX0001]	ZGP323LAP2804G [DX0001]
ZGP323LAP2808C [DX0001]	ZGP323LAP2808G [DX0001]
ZGP323LAP2816C [DX0001]	ZGP323LAP2816G [DX0001]
ZGP323LAP2832C [DX0001]	ZGP323LAP2832G [DX0001]
ZGP323LAP4004C [DX0001]	ZGP323LAP4004G [DX0001]
ZGP323LAP4008C [DX0001]	ZGP323LAP4008G [DX0001]
ZGP323LAP4016C [DX0001]	ZGP323LAP4016G [DX0001]
ZGP323LAP4032C [DX0001]	ZGP323LAP4032G [DX0001]
ZGP323LAS2004C@SOIC20 [DX1033]	ZGP323LAS2004G@SOIC20 [DX1033]
ZGP323LAS2008C@SOIC20 [DX1033]	ZGP323LAS2008G@SOIC20 [DX1033]
ZGP323LAS2016C@SOIC20 [DX1033]	ZGP323LAS2016G@SOIC20 [DX1033]
ZGP323LAS2032C@SOIC20 [DX1033]	ZGP323LAS2032G@SOIC20 [DX1033]
ZGP323LAS2804C@SOIC28 [DX1033]	ZGP323LAS2804G@SOIC28 [DX1033]
ZGP323LAS2808C@SOIC28 [DX1033]	ZGP323LAS2808G@SOIC28 [DX1033]
ZGP323LAS2816C@SOIC28 [DX1033]	ZGP323LAS2816G@SOIC28 [DX1033]
ZGP323LAS2832C@SOIC28 [DX1033]	ZGP323LAS2832G@SOIC28 [DX1033]
ZGP323LEH2004C@SSOP20 [DX1026]	ZGP323LEH2004G@SSOP20 [DX1026]
ZGP323LEH2008C@SSOP20 [DX1026]	ZGP323LEH2008G@SSOP20 [DX1026]

ZGP323LEH2016C@SSOP20 [DX1026]	ZGP323LEH2016G@SSOP20 [DX1026]
ZGP323LEH2032C@SSOP20 [DX1026]	ZGP323LEH2032G@SSOP20 [DX1026]
ZGP323LEH2804C@SSOP28 [DX1026]	ZGP323LEH2804G@SSOP28 [DX1026]
ZGP323LEH2808C@SSOP28 [DX1026]	ZGP323LEH2808G@SSOP28 [DX1026]
ZGP323LEH2816C@SSOP28 [DX1026]	ZGP323LEH2816G@SSOP28 [DX1026]
ZGP323LEH2832C@SSOP28 [DX1026]	ZGP323LEH2832G@SSOP28 [DX1026]
ZGP323LEH4804C@SSOP48 [DX1028]	ZGP323LEH4804G@SSOP48 [DX1028]
ZGP323LEH4808C@SSOP48 [DX1028]	ZGP323LEH4808G@SSOP48 [DX1028]
ZGP323LEH4816C@SSOP48 [DX1028]	ZGP323LEH4816G@SSOP48 [DX1028]
ZGP323LEH4832C@SSOP48 [DX1028]	ZGP323LEH4832G@SSOP48 [DX1028]
ZGP323LEP2004C [DX0001]	ZGP323LEP2004G [DX0001]
ZGP323LEP2008C [DX0001]	ZGP323LEP2008G [DX0001]
ZGP323LEP2016C [DX0001]	ZGP323LEP2016G [DX0001]
ZGP323LEP2032C [DX0001]	ZGP323LEP2032G [DX0001]
ZGP323LEP2804C [DX0001]	ZGP323LEP2804G [DX0001]
ZGP323LEP2808C [DX0001]	ZGP323LEP2808G [DX0001]
ZGP323LEP2816C [DX0001]	ZGP323LEP2816G [DX0001]
ZGP323LEP2832C [DX0001]	ZGP323LEP2832G [DX0001]
ZGP323LEP4004C [DX0001]	ZGP323LEP4004G [DX0001]
ZGP323LEP4008C [DX0001]	ZGP323LEP4008G [DX0001]
ZGP323LEP4016C [DX0001]	ZGP323LEP4016G [DX0001]
ZGP323LEP4032C [DX0001]	ZGP323LEP4032G [DX0001]
ZGP323LES2004C@SOIC20 [DX1033]	ZGP323LES2004G@SOIC20 [DX1033]
ZGP323LES2008C@SOIC20 [DX1033]	ZGP323LES2008G@SOIC20 [DX1033]
ZGP323LES2016C@SOIC20 [DX1033]	ZGP323LES2016G@SOIC20 [DX1033]
ZGP323LES2032C@SOIC20 [DX1033]	ZGP323LES2032G@SOIC20 [DX1033]
ZGP323LES2804C@SOIC28 [DX1033]	ZGP323LES2804G@SOIC28 [DX1033]
ZGP323LES2808C@SOIC28 [DX1033]	ZGP323LES2808G@SOIC28 [DX1033]
ZGP323LES2816C@SOIC28 [DX1033]	ZGP323LES2816G@SOIC28 [DX1033]
ZGP323LES2832C@SOIC28 [DX1033]	ZGP323LES2832G@SOIC28 [DX1033]
ZGP323LSH2004C@SSOP20 [DX1026]	ZGP323LSH2004G@SSOP20 [DX1026]
ZGP323LSH2008C@SSOP20 [DX1026]	ZGP323LSH2008G@SSOP20 [DX1026]
ZGP323LSH2016C@SSOP20 [DX1026]	ZGP323LSH2016G@SSOP20 [DX1026]
ZGP323LSH2032C@SSOP20 [DX1026]	ZGP323LSH2032G@SSOP20 [DX1026]
ZGP323LSH2804C@SSOP28 [DX1026]	ZGP323LSH2804G@SSOP28 [DX1026]
ZGP323LSH2808C@SSOP28 [DX1026]	ZGP323LSH2808G@SSOP28 [DX1026]
ZGP323LSH2816C@SSOP28 [DX1026]	ZGP323LSH2816G@SSOP28 [DX1026]
ZGP323LSH2832C@SSOP28 [DX1026]	ZGP323LSH2832G@SSOP28 [DX1026]
ZGP323LSH4804C@SSOP48 [DX1028]	ZGP323LSH4804G@SSOP48 [DX1028]
ZGP323LSH4808C@SSOP48 [DX1028]	ZGP323LSH4808G@SSOP48 [DX1028]
ZGP323LSH4816C@SSOP48 [DX1028]	ZGP323LSH4816G@SSOP48 [DX1028]
ZGP323LSH4832C@SSOP48 [DX1028]	ZGP323LSH4832G@SSOP48 [DX1028]
ZGP323LSK2032E [DX0001]	ZGP323LSK2032G [DX0001]
ZGP323LSK2832E [DX0001]	ZGP323LSK2832G [DX0001]
ZGP323LSK4032E [DX0001]	ZGP323LSK4032G [DX0001]
ZGP323LSP2004C [DX0001]	ZGP323LSP2004G [DX0001]
ZGP323LSP2008C [DX0001]	ZGP323LSP2008G [DX0001]
ZGP323LSP2016C [DX0001]	ZGP323LSP2016G [DX0001]

ZGP323LSP2032C [DX0001]	ZGP323LSP2032G [DX0001]
ZGP323LSP2804C [DX0001]	ZGP323LSP2804G [DX0001]
ZGP323LSP2808C [DX0001]	ZGP323LSP2808G [DX0001]
ZGP323LSP2816C [DX0001]	ZGP323LSP2816G [DX0001]
ZGP323LSP2832C [DX0001]	ZGP323LSP2832G [DX0001]
ZGP323LSP4004C [DX0001]	ZGP323LSP4004G [DX0001]
ZGP323LSP4008C [DX0001]	ZGP323LSP4008G [DX0001]
ZGP323LSP4016C [DX0001]	ZGP323LSP4016G [DX0001]
ZGP323LSP4032C [DX0001]	ZGP323LSP4032G [DX0001]
ZGP323LSS2004C@SOIC20 [DX1033]	ZGP323LSS2004G@SOIC20 [DX1033]
ZGP323LSS2008C@SOIC20 [DX1033]	ZGP323LSS2008G@SOIC20 [DX1033]
ZGP323LSS2016C@SOIC20 [DX1033]	ZGP323LSS2016G@SOIC20 [DX1033]
ZGP323LSS2032C@SOIC20 [DX1033]	ZGP323LSS2032G@SOIC20 [DX1033]
ZGP323LSS2804C@SOIC28 [DX1033]	ZGP323LSS2804G@SOIC28 [DX1033]
ZGP323LSS2808C@SOIC28 [DX1033]	ZGP323LSS2808G@SOIC28 [DX1033]
ZGP323LSS2816C@SOIC28 [DX1033]	ZGP323LSS2816G@SOIC28 [DX1033]
ZGP323LSS2832C@SOIC28 [DX1033]	ZGP323LSS2832G@SOIC28 [DX1033]
ZLF645E0H2032G@SSOP20 [DX1026]	ZLF645E0H2064G@SSOP20 [DX1026]
ZLF645E0H2832G@SSOP28 [DX1026]	ZLF645E0H2864G@SSOP28 [DX1026]
ZLF645E0P2032G [DX0001]	ZLF645E0P2064G [DX0001]
ZLF645E0P2832G [DX0001]	ZLF645E0P2864G [DX0001]
ZLF645E0Q2032G@QFN20 [DX4013]	ZLF645E0Q2064G@QFN20 [DX4013]
ZLF645E0S2032G@SOIC20 [DX1033]	ZLF645E0S2064G@SOIC20 [DX1033]
ZLF645E0S2832G@SOIC28 [DX1033]	ZLF645E0S2864G@SOIC28 [DX1033]
ZLF645S0H2032G@SSOP20 [DX1026]	ZLF645S0H2064G@SSOP20 [DX1026]
ZLF645S0H2832G@SSOP28 [DX1026]	ZLF645S0H2864G@SSOP28 [DX1026]
ZLF645S0P2032G [DX0001]	ZLF645S0P2064G [DX0001]
ZLF645S0P2832G [DX0001]	ZLF645S0P2864G [DX0001]
ZLF645S0Q2032G@QFN20 [DX4013]	ZLF645S0Q2064G@QFN20 [DX4013]
ZLF645S0S2032G@SOIC20 [DX1033]	ZLF645S0S2064G@SOIC20 [DX1033]
ZLF645S0S2832G@SOIC28 [DX1033]	ZLF645S0S2864G@SOIC28 [DX1033]
ZLP12840H2028C@SSOP20 [DX1026]	ZLP12840H2028G@SSOP20 [DX1026]
ZLP12840H2032C@SSOP20 [DX1026]	ZLP12840H2032G@SSOP20 [DX1026]
ZLP12840H2064C@SSOP20 [DX1026]	ZLP12840H2064G@SSOP20 [DX1026]
ZLP12840H2096C@SSOP20 [DX1026]	ZLP12840H2096G@SSOP20 [DX1026]
ZLP12840H2828C@SSOP28 [DX1026]	ZLP12840H2828G@SSOP28 [DX1026]
ZLP12840H2832C@SSOP28 [DX1026]	ZLP12840H2832G@SSOP28 [DX1026]
ZLP12840H2864C@SSOP28 [DX1026]	ZLP12840H2864G@SSOP28 [DX1026]
ZLP12840H2896C@SSOP28 [DX1026]	ZLP12840H2896G@SSOP28 [DX1026]
ZLP12840P2028C [DX0001]	ZLP12840P2028G [DX0001]
ZLP12840P2032C [DX0001]	ZLP12840P2032G [DX0001]
ZLP12840P2064C [DX0001]	ZLP12840P2064G [DX0001]
ZLP12840P2096C [DX0001]	ZLP12840P2096G [DX0001]
ZLP12840P2828C [DX0001]	ZLP12840P2828G [DX0001]
ZLP12840P2832C [DX0001]	ZLP12840P2832G [DX0001]
ZLP12840P2864C [DX0001]	ZLP12840P2864G [DX0001]
ZLP12840P2896C [DX0001]	ZLP12840P2896G [DX0001]
ZLP12840S2028C@SOIC20 [DX1033]	ZLP12840S2028G@SOIC20 [DX1033]

ZLP12840S2032C@SOIC20 [DX1033]
ZLP12840S2032G@SOIC20 [DX1033]
ZLP12840S2064C@SOIC20 [DX1033]
ZLP12840S2064G@SOIC20 [DX1033]
ZLP12840S2096C@SOIC20 [DX1033]
ZLP12840S2096G@SOIC20 [DX1033]
ZLP12840S2828C@SOIC28 [DX1033]
ZLP12840S2828G@SOIC28 [DX1033]
ZLP12840S2832C@SOIC28 [DX1033]
ZLP12840S2832G@SOIC28 [DX1033]
ZLP12840S2864C@SOIC28 [DX1033]
ZLP12840S2864G@SOIC28 [DX1033]
ZLP12840S2896C@SOIC28 [DX1033]
ZLP12840S2896G@SOIC28 [DX1033]
ZLP32300H2004C@SSOP20 [DX1026]
ZLP32300H2004G@SSOP20 [DX1026]
ZLP32300H2008C@SSOP20 [DX1026]
ZLP32300H2008G@SSOP20 [DX1026]
ZLP32300H2016C@SSOP20 [DX1026]
ZLP32300H2016G@SSOP20 [DX1026]
ZLP32300H2032C@SSOP20 [DX1026]
ZLP32300H2032G@SSOP20 [DX1026]
ZLP32300H2804C@SSOP28 [DX1026]
ZLP32300H2804G@SSOP28 [DX1026]
ZLP32300H2808C@SSOP28 [DX1026]
ZLP32300H2808G@SSOP28 [DX1026]
ZLP32300H2816C@SSOP28 [DX1026]
ZLP32300H2816G@SSOP28 [DX1026]
ZLP32300H2832C@SSOP28 [DX1026]
ZLP32300H2832G@SSOP28 [DX1026]
ZLP32300H4804C@SSOP48 [DX1028]
ZLP32300H4804G@SSOP48 [DX1028]
ZLP32300H4808C@SSOP48 [DX1028]
ZLP32300H4808G@SSOP48 [DX1028]
ZLP32300H4816C@SSOP48 [DX1028]
ZLP32300H4816G@SSOP48 [DX1028]
ZLP32300H4832C@SSOP48 [DX1028]
ZLP32300H4832G@SSOP48 [DX1028]
ZLP32300P2004C [DX0001]
ZLP32300P2004G [DX0001]
ZLP32300P2008C [DX0001]
ZLP32300P2008G [DX0001]
ZLP32300P2016C [DX0001]
ZLP32300P2016G [DX0001]
ZLP32300P2032C [DX0001]
ZLP32300P2032G [DX0001]
ZLP32300P2804C [DX0001]
ZLP32300P2804G [DX0001]
ZLP32300P2808C [DX0001]
ZLP32300P2808G [DX0001]
ZLP32300P2816C [DX0001]
ZLP32300P2816G [DX0001]
ZLP32300P2832C [DX0001]
ZLP32300P2832G [DX0001]
ZLP32300P4004C [DX0001]
ZLP32300P4004G [DX0001]
ZLP32300P4008C [DX0001]
ZLP32300P4008G [DX0001]
ZLP32300P4016C [DX0001]
ZLP32300P4016G [DX0001]
ZLP32300P4032C [DX0001]
ZLP32300P4032G [DX0001]
ZLP32300S2004C@SOIC20 [DX1033]
ZLP32300S2004G@SOIC20 [DX1033]
ZLP32300S2008C@SOIC20 [DX1033]
ZLP32300S2008G@SOIC20 [DX1033]
ZLP32300S2016C@SOIC20 [DX1033]
ZLP32300S2016G@SOIC20 [DX1033]
ZLP32300S2032C@SOIC20 [DX1033]
ZLP32300S2032G@SOIC20 [DX1033]
ZLP32300S2804C@SOIC28 [DX1033]
ZLP32300S2804G@SOIC28 [DX1033]
ZLP32300S2808C@SOIC28 [DX1033]
ZLP32300S2808G@SOIC28 [DX1033]
ZLP32300S2816C@SOIC28 [DX1033]
ZLP32300S2816G@SOIC28 [DX1033]
ZLP32300S2832C@SOIC28 [DX1033]
ZLP32300S2832G@SOIC28 [DX1033]

MAXWELL

E(E)PROM/FRAM/NVRAM

28C010 [DX0001]
28C010@PLCC32 [DX2032]
28C010@TSOP32 [DX1002]
28C010T [DX0001]
28C010T@PLCC32 [DX2032]
28C010T@TSOP32 [DX1002]

28C011 [DX0001]
28C011@PLCC32 [DX2032]
28C011@TSOP32 [DX1002]
28C011T [DX0001]
28C011T@PLCC32 [DX2032]
28C011T@TSOP32 [DX1002]

MEGAWIN

E(E)PROM/FRAM/NVRAM

MM25SB512@SOIC8 [DX1045]
MM29F040 [DX0001]
MM29F040@PLCC32 [DX2032]
MM29F040@TSOP32 [DX1002]
MM29LF040 [DX0001]
MM29LF040@PLCC32 [DX2032]
MM29LF040@TSOP32 [DX1002]

MICROCONTROLLER

MA801AE [DX0001]
MA801AS@SOP20 [DX1033]
MA801AT@TSSOP20 [DX1001]
MA802AE [DX0001]
MA802AS@SOP20 [DX1033]
MA802AT@TSSOP20 [DX1001]
MA803AD@LQFP32 [DX3001]
MA803AE [DX0001]
MA803AE2 [DX0001]
MA803AS@SOP20 [DX1033]
MA803AS2@SOP28 [DX1033]
MA803AT@TSSOP20 [DX1001]
MA804AD@LQFP32 [DX3001]
MA804AE [DX0001]
MA804AE2 [DX0001]
MA804AS@SOP20 [DX1033]
MA804AS2@SOP28 [DX1033]
MA804AT@TSSOP20 [DX1001]
MA805-24A [DX0001]
MA805-24A@QFP44 [DX3003]
MA805-24A@QFP48 [DX3007]
MA805-32A [DX0001]
MA805-32A@QFP44 [DX3003]
MA805-32A@QFP48 [DX3007]
MA805-64A [DX0001]
MA805-64A@QFP44 [DX3003]
MA805-64A@QFP48 [DX3007]
MA806-24A [DX0001]
MA806-24A@QFP44 [DX3003]
MA806-24A@QFP48 [DX3007]
MA806-32A [DX0001]
MA806-32A@QFP44 [DX3003]
MA806-32A@QFP48 [DX3007]
MA806-64A [DX0001]
MA806-64A@QFP44 [DX3003]
MA806-64A@QFP48 [DX3007]
MA807A@QFP44 [DX3003]
MA808A@QFP44 [DX3003]
MA816A@QFP44 [DX3003]
MA82FG5C32A-Q48 [DX3007]
MA82FG5C32A-Q64 [DX3011]
MA82FG5C64A-Q48 [DX3007]
MA82FG5C64A-Q64 [DX3011]
MA82G5A32AC@QFP64 [DX3011]
MA82G5A32AD@QFP48 [DX3007]
MA82G5A64AC@QFP64 [DX3011]
MA82G5A64AD@QFP48 [DX3007]
MA82G5B16A@QFP32 [DX3001]
MA82G5B16A@SOP20 [DX1033]
MA82G5B16A@SOP28 [DX1033]
MA82G5B32A@QFP32 [DX3001]
MA82G5B32A@SOP20 [DX1033]
MA82G5B32A@SOP28 [DX1033]
MA86E104AS@SOP16 [DX1016]
MA86E104AS@SOP20 [DX1033]
MA86E104AS@SOP8 [DX1016]
MA86E508AS@SOP16 [DX1016]
MA86E508AS@SOP20 [DX1033]
MA86E508AS@SOP28 [DX1033]
MA86L104AS@SOP16 [DX1016]
MA86L104AS@SOP20 [DX1033]
MA86L104AS@SOP8 [DX1016]

MA86L508AS@SOP16 [DX1016]
MA86L508AS@SOP20 [DX1033]
MA86L508AS@SOP28 [DX1033]
MG82FE308AD@QFP48 [DX3007]
MG82FE316AD@QFP64 [DX3085]
MG82FE532AD@QFP48 [DX3007]
MG82FE532AE [DX0001]
MG82FE532AF@QFP44 [DX3002]
MG82FE532AP@PLCC44 [DX2044]
MG82FE564AD@QFP48 [DX3007]
MG82FE564AE [DX0001]
MG82FE564AF@QFP44 [DX3002]
MG82FE564AP@PLCC44 [DX2044]
MG82FG5A32AD@QFP48 [DX3007]
MG82FG5A32AD@QFP64 [DX3085]
MG82FG5A64AD@QFP48 [DX3007]
MG82FG5A64AD@QFP64 [DX3085]
MG82FG5B16AD@QFP32 [DX3001]
MG82FG5B32AD@QFP32 [DX3001]
MG82FL308AD@QFP48 [DX3007]
MG82FL316AD@QFP64 [DX3085]
MG82FL532AD@QFP48 [DX3007]
MG82FL532AE [DX0001]
MG82FL532AF@QFP44 [DX3002]
MG82FL532AP@PLCC44 [DX2044]
MG82FL564AD@QFP48 [DX3007]
MG82FL564AE [DX0001]
MG82FL564AF@QFP44 [DX3002]
MG82FL564AP@PLCC44 [DX2044]
MG84FG516AD@QFP48 [DX3007]
MG84FG516AD@QFP64 [DX3085]
MG86FE104AS@SOP16 [DX1016]
MG86FE104AS@SOP20 [DX1033]
MG86FE104AS@SOP8 [DX1016]
MG86FE508AS@SOP20 [DX1033]
MG86FE508AS@SOP28 [DX1033]
MG86FL104AS@SOP16 [DX1016]
MG86FL104AS@SOP20 [DX1033]
MG86FL104AS@SOP8 [DX1016]
MG86FL508AS@SOP20 [DX1033]
MG86FL508AS@SOP28 [DX1033]
MG87FE2051AE@DIP16 [DX0001]
MG87FE2051AE@DIP18 [DX0001]
MG87FE2051AE@DIP20 [DX0001]
MG87FE2051AS@SOP16 [DX1033]
MG87FE2051AS@SOP18 [DX1033]
MG87FE2051AS@SOP20 [DX1033]
MG87FE4051AE@DIP16 [DX0001]
MG87FE4051AE@DIP18 [DX0001]
MG87FE4051AE@DIP20 [DX0001]
MG87FE4051AS@SOP16 [DX1033]
MG87FE4051AS@SOP18 [DX1033]
MG87FE4051AS@SOP20 [DX1033]
MG87FE51AE [DX0001]
MG87FE51AF@TQFP44 [DX3002]
MG87FE51AP@PLCC44 [DX2044]
MG87FE52AE [DX0001]
MG87FE52AF@TQFP44 [DX3002]
MG87FE52AP@PLCC44 [DX2044]
MG87FE6051AE@DIP16 [DX0001]
MG87FE6051AE@DIP18 [DX0001]
MG87FE6051AE@DIP20 [DX0001]
MG87FE6051AS@SOP16 [DX1033]
MG87FE6051AS@SOP18 [DX1033]
MG87FE6051AS@SOP20 [DX1033]
MG87FL2051AE@DIP16 [DX0001]
MG87FL2051AE@DIP18 [DX0001]
MG87FL2051AE@DIP20 [DX0001]
MG87FL2051AS@SOP16 [DX1033]
MG87FL2051AS@SOP18 [DX1033]
MG87FL2051AS@SOP20 [DX1033]
MG87FL4051AE@DIP16 [DX0001]
MG87FL4051AE@DIP18 [DX0001]
MG87FL4051AE@DIP20 [DX0001]
MG87FL4051AS@SOP16 [DX1033]
MG87FL4051AS@SOP18 [DX1033]
MG87FL4051AS@SOP20 [DX1033]
MG87FL51AE [DX0001]
MG87FL51AF@TQFP44 [DX3002]
MG87FL51AP@PLCC44 [DX2044]
MG87FL52AE [DX0001]
MG87FL52AF@TQFP44 [DX3002]
MG87FL52AP@PLCC44 [DX2044]
MG87FL6051AE@DIP16 [DX0001]
MG87FL6051AE@DIP18 [DX0001]
MG87FL6051AE@DIP20 [DX0001]
MG87FL6051AS@SOP16 [DX1033]
MG87FL6051AS@SOP18 [DX1033]
MG87FL6051AS@SOP20 [DX1033]
MPC82E52AE [DX0001]
MPC82E52AS@SOP20 [DX1033]
MPC82E52AT@SSOP20 [DX1001]
MPC82E54AE [DX0001]
MPC82E54AE2 [DX0001]
MPC82E54AP@PLCC32 [DX2032]
MPC82E54AS@SOP20 [DX1033]

MPC82E54AS2@SOP28 [DX1033]
MPC82E54AT@SSOP20 [DX1001]
MPC82E54AT2@SSOP28 [DX1001]
MPC82G516AD@LQFP48 [DX3007]
MPC82G516AE [DX0001]
MPC82G516AF@PQFP44 [DX3002]
MPC82G516AP@PLCC44 [DX2044]
MPC82L52AE [DX0001]
MPC82L52AS@SOP20 [DX1033]
MPC82L52AT@SSOP20 [DX1001]
MPC82L54AE [DX0001]
MPC82L54AE2 [DX0001]
MPC82L54AP@PLCC32 [DX2032]
MPC82L54AS@SOP20 [DX1033]
MPC82L54AS2@SOP28 [DX1033]
MPC82L54AT@SSOP20 [DX1001]
MPC82L54AT2@SSOP28 [DX1001]
MPC89E515AE [DX0001]
MPC89E515AF@PQFP44 [DX3002]
MPC89E515AP@PLCC44 [DX2044]
MPC89E51AE [DX0001]
MPC89E51AF@PQFP44 [DX3002]
MPC89E51AP@PLCC44 [DX2044]
MPC89E52AE [DX0001]
MPC89E52AF@PQFP44 [DX3002]
MPC89E52AP@PLCC44 [DX2044]
MPC89E53AE [DX0001]
MPC89E53AF@PQFP44 [DX3002]
MPC89E53AP@PLCC44 [DX2044]
MPC89E54AE [DX0001]
MPC89E54AF@PQFP44 [DX3002]
MPC89E54AP@PLCC44 [DX2044]
MPC89E58AE [DX0001]
MPC89E58AF@PQFP44 [DX3002]
MPC89E58AP@PLCC44 [DX2044]
MPC89L515AE [DX0001]
MPC89L515AF@PQFP44 [DX3002]
MPC89L515AP@PLCC44 [DX2044]
MPC89L516X2 [DX0001]
MPC89L516X2@PLCC44 [DX2044]
MPC89L516X2@TQFP44 [DX3003]
MPC89L51AE [DX0001]
MPC89L51AF@PQFP44 [DX3002]
MPC89L51AP@PLCC44 [DX2044]
MPC89L52AE [DX0001]
MPC89L52AF@PQFP44 [DX3002]
MPC89L52AP@PLCC44 [DX2044]
MPC89L53AE [DX0001]
MPC89L53AF@PQFP44 [DX3002]
MPC89L53AP@PLCC44 [DX2044]
MPC89L54AE [DX0001]
MPC89L54AF@PQFP44 [DX3002]
MPC89L54AP@PLCC44 [DX2044]
MPC89L556X2 [DX0001]
MPC89L556X2@PLCC44 [DX2044]
MPC89L556X2@TQFP44 [DX3003]
MPC89L58AE [DX0001]
MPC89L58AF@PQFP44 [DX3002]
MPC89L58AP@PLCC44 [DX2044]

MEMC

MICROCONTROLLER

ME16F32G@LQFP64 [DX3012]
ME16F32G@QFP64 [DX3012]
ME16F34G@LQFP64 [DX3012]
ME16F34G@QFP64 [DX3012]
ME16F38G@LQFP64 [DX3012]
ME16F38G@QFP64 [DX3012]
ME16F48@LQFP100 [DX3021]
ME16F48@QFP100 [DX3021]
ME16F49@LQFP100 [DX3021]
ME16F49@QFP100 [DX3021]

MEMOCOM

E(E)PROM/FRAM/NVRAM

KI01602AB(Ga1)@FBGA66 [DX5005]
KI01602AB(Gb1)@FBGA66 [DX5026]

KI01602AT(Ga1)@FBGA66 [DX5005]
KI01604AB(Ga1)@FBGA58 [DX5005]
KI01604AT(Ga1)@FBGA58 [DX5005]
KI01608AB(Ga1)@FBGA58 [DX5005]
KI01608AT(Ga1)@FBGA58 [DX5005]
KI03204AB(Ga1)@FBGA58 [DX5005]
KI03204AT(Ga1)@FBGA58 [DX5005]
KI03204BB@FBGA58 [DX5005]
KI03208AB(Ga1)@FBGA58 [DX5005]
KI03208AT(Ga1)@FBGA58 [DX5005]
KI03208BB@FBGA58 [DX5005]
KI03216AB(Ha1)@FBGA88 [DX5005]
KI06416AB(Ha1)@FBGA88 [DX5005]
KIB2832AU(Ha1)@FBGA88 [DX5005]
KIB6432AT(Ha1)@FBGA88 [DX5005]
KIP2864AU(Ha1)@FBGA88 [DX5005]
KIP6432AT(Ha1)@FBGA88 [DX5005]
KIX2864EU(HY1)@FBGA56 [DX5094]
KS01602AB(Gh)@FBGA56 [DX5045]
KS01604AB(Gh)@FBGA56 [DX5045]
KS03204AB(Gh)@FBGA56 [DX5045]
KS03204CB@FBGA56 [DX5045]
KS03208AB(Gh)@FBGA56 [DX5045]
KS03208BB@FBGA56 [DX5045]
KS03216AB(Hh1)@FBGA56 [DX5045]
KS06416AB(Hh1)@FBGA56 [DX5045]
KSP2832AU(Hs1)@FBGA64 [DX5001]
KSP2864AU(Hs1)@FBGA64 [DX5001]
KSP3216BT@FBGA56 [DX5045]
KSP6416BT@FBGA56 [DX5045]
KSP6432AT@FBGA56 [DX5045]
KI01602AT(Gb1)@FBGA66 [DX5026]
KI01604AB(Gb1)@FBGA66 [DX5005]
KI01604AT(Gb1)@FBGA66 [DX5005]
KI01608AB(Gb1)@FBGA66 [DX5005]
KI01608AT(Gb1)@FBGA66 [DX5005]
KI03204AB(Gb1)@FBGA66 [DX5005]
KI03204AT(Gb1)@FBGA66 [DX5005]
KI03204BT@FBGA58 [DX5005]
KI03208AB(Gb1)@FBGA66 [DX5005]
KI03208AT(Gb1)@FBGA66 [DX5005]
KI03208BT@FBGA58 [DX5005]
KI03216AT(Ha1)@FBGA88 [DX5005]
KI06416AT(Ha1)@FBGA88 [DX5005]
KIB2864AU(Ha1)@FBGA88 [DX5005]
KIP2832AU(Ha1)@FBGA88 [DX5005]
KIP6432AB(Ha1)@FBGA88 [DX5005]
KIX2832DU(HY1)@FBGA56 [DX5094]
KIX6432AT(HY1)@FBGA56 [DX5094]
KS01602AT(Gh)@FBGA56 [DX5045]
KS01604AT(Gh)@FBGA56 [DX5045]
KS03204AT(Gh)@FBGA56 [DX5045]
KS03204CT@FBGA56 [DX5045]
KS03208AT(Gh)@FBGA56 [DX5045]
KS03208BT@FBGA56 [DX5045]
KS03216AT(Hh1)@FBGA56 [DX5045]
KS06416AT(Hh1)@FBGA56 [DX5045]
KSP2832EU(HT1)@FBGA84 [DX5001]
KSP3216BB@FBGA56 [DX5045]
KSP6416BB@FBGA56 [DX5045]
KSP6432AB@FBGA56 [DX5045]
KTF29028AU@TSOP56 [DX1011]

MICON

MICROCONTROLLER

MDT10P21(dip18) [DX0001]
MDT10P21(dip22) [DX0001]
MDT10P21@SOP20 [DX1033]
MDT10P22(dip18) [DX0001]
MDT10P22(dip22) [DX0001]
MDT10P22@SOP20 [DX1033]
MDT10P23(dip18) [DX0001]
MDT10P23(dip22) [DX0001]
MDT10P23@SOP20 [DX1033]
MDT10P41A1 [DX0001]
MDT10P41A2 [DX0001]
MDT10P21(dip20) [DX0001]
MDT10P21@SOP18 [DX1033]
MDT10P21@SOP24 [DX1033]
MDT10P22(dip20) [DX0001]
MDT10P22@SOP18 [DX1033]
MDT10P22@SOP24 [DX1033]
MDT10P23(dip20) [DX0001]
MDT10P23@SOP18 [DX1033]
MDT10P23@SOP24 [DX1033]
MDT10P41A1@SOP16 [DX1033]
MDT10P41A2@SOP16 [DX1033]

MDT10P43P11 [DX0001]
MDT10P43P21 [DX0001]
MDT10P43S11@SOP18 [DX1033]
MDT10P43S21@SOP20 [DX1033]
MDT10P55A1 [DX0001]
MDT10P55A1@SOP14 [DX1030]
MDT10P55A2 [DX0001]
MDT10P55A2@SOP14 [DX1030]
MDT10P55A3 [DX0001]
MDT10P55A3@SOP14 [DX1030]
MDT10P55A4 [DX0001]
MDT10P55A4@SOP14 [DX1030]
MDT10P55B1 [DX0001]
MDT10P55B1@SOP14 [DX1030]
MDT10P55B2 [DX0001]
MDT10P55B2@SOP14 [DX1030]
MDT10P55B3 [DX0001]
MDT10P55B3@SOP14 [DX1030]
MDT10P55B4 [DX0001]
MDT10P55B4@SOP14 [DX1030]
MDT10P61 [DX0001]
MDT10P61@SOP18 [DX1033]
MDT10P61@SSOP20 [DX1026]
MDT10P62 [DX0001]
MDT10P62@SOP28 [DX1033]
MDT10P62@SSOP28 [DX1026]
MDT10P621 [DX0001]
MDT10P621@SOP28 [DX1033]
MDT10P621@SSOP28 [DX1026]
MDT10P64 [DX0001]
MDT10P64@PLCC44 [DX2044]
MDT10P64@QFP44 [DX3046]
MDT10P65(dip28) [DX0001]
MDT10P65(dip42) [DX0001]
MDT10P65@SDIP42 [DX0042]
MDT10P65@SOP28 [DX1033]
MDT10P651 [DX0001]
MDT10P651@PLCC44 [DX2044]
MDT10P651@QFP44 [DX3046]
MDT10P65A1@QFP44 [DX3046]
MDT10P65A2@QFP44 [DX3046]
MDT10P72 [DX0001]
MDT10P72@SOP28 [DX1033]
MDT10P72@SSOP28 [DX1026]
MDT10P721 [DX0001]
MDT10P721@SOP28 [DX1033]
MDT10P721@SSOP28 [DX1026]
MDT10P73 [DX0001]
MDT10P73@SOP28 [DX1033]
MDT10P73@SSOP28 [DX1026]
MDT10P74 [DX0001]
MDT10P74@PLCC44 [DX2044]
MDT10P74@QFP44 [DX3046]
MDT2005 [DX0001]
MDT2005@SOP18 [DX1033]
MDT2005@SSOP20 [DX1026]
MDT2010 [DX0001]
MDT2010@SOP18 [DX1033]
MDT2010@SSOP20 [DX1026]
MDT2020 [DX0001]
MDT2020@SOP28 [DX1033]
MDT2020@SSOP28 [DX1026]
MDT2030 [DX0001]
MDT2030@SOP18 [DX1033]
MDT2030@SSOP20 [DX1026]
MDT2050 [DX0001]
MDT2050@SOP18 [DX1033]
MDT2050@SSOP20 [DX1026]
MDT2051 [DX0001]
MDT2051@SOP18 [DX1033]
MDT2051@SSOP20 [DX1026]
MDT2060 [DX0001]
MDT2060@SOP18 [DX1033]
MDT2060@SSOP20 [DX1026]

MICROCHIP

E(E)PROM/FRAM/NVRAM

23A256 [DX0001]
23A256@SOIC8 [DX1045]
23A256@TSSOP8 [DX1059]
23A640 [DX0001]
23A640@SOIC8 [DX1045]
23A640@TSSOP8 [DX1059]
23K256 [DX0001]
23K256@SOIC8 [DX1045]
23K256@TSSOP8 [DX1059]
23K640 [DX0001]

23K640@SOIC8 [DX1045]
23K640@TSSOP8 [DX1059]
24AA00 [DX0001]
24AA00@DFN8 [DX4047]
24AA00@SOIC8 [DX1045]
24AA00@SOT-23 [DX1041]
24AA00@TSSOP8 [DX1059]
24AA01 [DX0001]
24AA01@DFN8 [DX4047]
24AA01@SOIC8 [DX1045]
24AA01@TSSOP8 [DX1059]
24AA014 [DX0001]
24AA014@SOIC8 [DX1045]
24AA014@TSSOP8 [DX1059]
24AA02 [DX0001]
24AA02@DFN8 [DX4047]
24AA02@MSOP8 [DX1015]
24AA02@SOIC8 [DX1045]
24AA02@SOT-23-5 [DX1041]
24AA02@TSSOP8 [DX1059]
24AA024 [DX0001]
24AA024@DFN8 [DX4002]
24AA024@MSOP8 [DX1015]
24AA024@SOIC8 [DX1045]
24AA024@TSSOP8 [DX1059]
24AA025 [DX0001]
24AA025@DFN8 [DX4002]
24AA025@MSOP8 [DX1015]
24AA025@SOIC8 [DX1045]
24AA025@TSSOP8 [DX1059]
24AA04 [DX0001]
24AA04@DFN8 [DX4047]
24AA04@SOIC8 [DX1045]
24AA04@TSSOP8 [DX1059]
24AA08 [DX0001]
24AA08@DFN8 [DX4047]
24AA08@SOIC8 [DX1045]
24AA08@TSSOP8 [DX1059]
24AA1025 [DX0001]
24AA1025@SOIC8 [DX1044]
24AA1025@TSSOP8 [DX1059]
24AA1026 [DX0001]
24AA1026@SOIC8 [DX1044]
24AA1026@TSSOP8 [DX1044]
24AA128 [DX0001]
24AA128@DFN8 [DX4047]
24AA128@MSOP8 [DX1015]
24AA128@SOIC8 [DX1045]
24AA128@TSSOP14 [DX1000]
24AA128@TSSOP8 [DX1059]
24AA16 [DX0001]
24AA16@DFN8 [DX4047]
24AA16@SOIC8 [DX1045]
24AA16@TSSOP8 [DX1059]
24AA164 [DX0001]
24AA164@SOIC8 [DX1045]
24AA164@TSSOP8 [DX1059]
24AA174 [DX0001]
24AA174@SOIC8 [DX1045]
24AA174@TSSOP8 [DX1059]
24AA256 [DX0001]
24AA256@DFN8 [DX4047]
24AA256@MSOP8 [DX1015]
24AA256@SOIC8 [DX1045]
24AA256@TSSOP14 [DX1000]
24AA256@TSSOP8 [DX1059]
24AA32 [DX0001]
24AA32(Rotated)@TSSOP8 [DX1059]
24AA32@DFN8 [DX4047]
24AA32@MSOP8 [DX1015]
24AA32@SOIC8 [DX1045]
24AA32@TSSOP8 [DX1059]
24AA32A [DX0001]
24AA32A(Rotated)@TSSOP8 [DX1059]
24AA32A@DFN8 [DX4047]
24AA32A@MSOP8 [DX1015]
24AA32A@SOIC8 [DX1045]
24AA32A@SOT-23 [DX1041]
24AA32A@TSSOP8 [DX1059]
24AA32AF [DX0001]
24AA32AF(Rotated)@TSSOP8 [DX1059]
24AA32AF@DFN8 [DX4047]
24AA32AF@MSOP8 [DX1015]
24AA32AF@SOIC8 [DX1045]
24AA32AF@TSSOP8 [DX1059]
24AA512 [DX0001]
24AA512@DFN8 [DX4005]
24AA512@SOIC8 [DX1044]
24AA512@TSSOP14 [DX1030]
24AA515 [DX0001]
24AA515@SOIC8 [DX1044]
24AA52 [DX0001]
24AA52@DFN8 [DX4002]
24AA52@MSOP8 [DX1015]
24AA52@SOIC8 [DX1045]

24AA52@TSSOP8 [DX1059]
24AA64 [DX0001]
24AA64(Rotated)@TSSOP8 [DX1059]
24AA64@DFN8 [DX4047]
24AA64@MSOP8 [DX1015]
24AA64@SOIC8 [DX1045]
24AA64@TSSOP8 [DX1059]
24AA64F [DX0001]
24AA64F(Rotated)@TSSOP8 [DX1059]
24AA64F@DFN8 [DX4047]
24AA64F@MSOP8 [DX1015]
24AA64F@SOIC8 [DX1045]
24AA64F@TSSOP8 [DX1059]
24AA65 [DX0001]
24AA65@DFN8 [DX4047]
24AA65@SOIC8 [DX1045]
24AA65@TSSOP8 [DX1059]
24C00 [DX0001]
24C00@DFN8 [DX4047]
24C00@SOIC8 [DX1045]
24C00@SOT-23 [DX1041]
24C00@TSSOP8 [DX1059]
24C01 [DX0001]
24C01A [DX0001]
24C01A@SOIC8 [DX1045]
24C01C [DX0001]
24C01C@SOIC8 [DX1045]
24C01C@TSSOP8 [DX1059]
24C02 [DX0001]
24C02A [DX0001]
24C02A@SOIC8 [DX1045]
24C02C [DX0001]
24C02C@SOIC8 [DX1045]
24C02C@TSSOP8 [DX1059]
24C04 [DX0001]
24C04A [DX0001]
24C04A@SOIC8 [DX1045]
24C04A@TSSOP8 [DX1059]
24C08 [DX0001]
24C08@SOIC8 [DX1045]
24C08B [DX0001]
24C08B@SOIC8 [DX1045]
24C16 [DX0001]
24C16@SOIC8 [DX1045]
24C16B [DX0001]
24C16B@SOIC8 [DX1045]
24C32 [DX0001]
24C32@DFN8 [DX4047]
24C32@SOIC8 [DX1045]
24C64 [DX0001]
24C64@DFN8 [DX4047]
24C64@SOIC8 [DX1045]
24C64@TSSOP8 [DX1059]
24C65 [DX0001]
24C65@DFN8 [DX4047]
24C65@SOIC8 [DX1045]
24FC1025 [DX0001]
24FC1025@SOIC8 [DX1044]
24FC1025@TSSOP8 [DX1059]
24FC1026 [DX0001]
24FC1026@SOIC8 [DX1044]
24FC1026@TSSOP8 [DX1044]
24FC128 [DX0001]
24FC128@DFN8 [DX4047]
24FC128@MSOP8 [DX1015]
24FC128@SOIC8 [DX1045]
24FC128@TSSOP14 [DX1000]
24FC128@TSSOP8 [DX1059]
24FC256 [DX0001]
24FC256@DFN8 [DX4047]
24FC256@MSOP8 [DX1015]
24FC256@SOIC8 [DX1045]
24FC256@TSSOP14 [DX1000]
24FC256@TSSOP8 [DX1059]
24FC32 [DX0001]
24FC32@DFN8 [DX4047]
24FC32@SOIC8 [DX1045]
24FC512 [DX0001]
24FC512@DFN8 [DX4005]
24FC512@SOIC8 [DX1044]
24FC512@TSSOP14 [DX1030]
24FC515 [DX0001]
24FC515@SOIC8 [DX1044]
24FC64 [DX0001]
24FC64(Rotated)@TSSOP8 [DX1059]
24FC64@DFN8 [DX4047]
24FC64@MSOP8 [DX1015]
24FC64@SOIC8 [DX1045]
24FC64@TSSOP8 [DX1059]
24FC65 [DX0001]
24FC65@DFN8 [DX4047]
24FC65@SOIC8 [DX1045]
24LC00 [DX0001]
24LC00@DFN8 [DX4047]
24LC00@SOIC8 [DX1045]
24LC00@SOT-23 [DX1041]

24LC00@TSSOP8 [DX1059]
24LC01 [DX0001]
24LC014 [DX0001]
24LC014@SOIC8 [DX1045]
24LC014@TSSOP8 [DX1059]
24LC01B [DX0001]
24LC01B@DFN8 [DX4047]
24LC01B@SOIC8 [DX1045]
24LC01B@TSSOP8 [DX1059]
24LC02 [DX0001]
24LC024 [DX0001]
24LC024@SOIC8 [DX1045]
24LC024@TSSOP8 [DX1059]
24LC025 [DX0001]
24LC025@SOIC8 [DX1045]
24LC025@TSSOP8 [DX1059]
24LC02B [DX0001]
24LC02B@DFN8 [DX4047]
24LC02B@MSOP8 [DX1015]
24LC02B@SOIC8 [DX1045]
24LC02B@SOT-23-5 [DX1041]
24LC02B@TSSOP8 [DX1059]
24LC04 [DX0001]
24LC04B [DX0001]
24LC04B@DFN8 [DX4047]
24LC04B@SOIC8 [DX1045]
24LC04B@TSSOP8 [DX1059]
24LC08 [DX0001]
24LC08B [DX0001]
24LC08B@DFN8 [DX4047]
24LC08B@SOIC8 [DX1045]
24LC08B@TSSOP8 [DX1059]
24LC1025 [DX0001]
24LC1025@SOIC8 [DX1044]
24LC1025@TSSOP8 [DX1059]
24LC1026 [DX0001]
24LC1026@SOIC8 [DX1044]
24LC1026@TSSOP8 [DX1044]
24LC128 [DX0001]
24LC128@DFN8 [DX4047]
24LC128@MSOP8 [DX1015]
24LC128@SOIC8 [DX1045]
24LC128@TSSOP14 [DX1000]
24LC128@TSSOP8 [DX1059]
24LC16 [DX0001]
24LC16@MSOP8 [DX1015]
24LC16@SOIC8 [DX1045]
24LC164 [DX0001]
24LC164@SOIC8 [DX1045]
24LC16B [DX0001]
24LC16B@DFN8 [DX4047]
24LC16B@SOIC8 [DX1045]
24LC16B@TSSOP8 [DX1059]
24LC174 [DX0001]
24LC174@SOIC8 [DX1045]
24LC21 [DX0001]
24LC21@SOIC8 [DX1045]
24LC21A [DX0001]
24LC21A@SOIC8 [DX1045]
24LC22A [DX0001]
24LC22A@SOIC8 [DX1045]
24LC256 [DX0001]
24LC256@DFN8 [DX4047]
24LC256@MSOP8 [DX1015]
24LC256@SOIC8(150mil) [DX1045]
24LC256@SOIC8(200mil) [DX1044]
24LC256@TSSOP14 [DX1000]
24LC256@TSSOP8 [DX1059]
24LC32 [DX0001]
24LC32@SOIC8 [DX1045]
24LC32A [DX0001]
24LC32A@DFN8 [DX4047]
24LC32A@SOIC8 [DX1045]
24LC32A@SOT-23 [DX1041]
24LC32A@TSSOP8 [DX1059]
24LC32AF [DX0001]
24LC32AF@DFN8 [DX4047]
24LC32AF@SOIC8 [DX1045]
24LC32AF@TSSOP8 [DX1059]
24LC512 [DX0001]
24LC512@DFN8 [DX4005]
24LC512@SOIC8(150 mil) [DX1045]
24LC512@SOIC8(200 mil) [DX1044]
24LC512@TSSOP14 [DX1030]
24LC515 [DX0001]
24LC515@SOIC8 [DX1044]
24LC64 [DX0001]
24LC64(Rotated)@TSSOP8 [DX1059]
24LC64(SM)@SOIC8 [DX1044]
24LC64@DFN8 [DX4047]
24LC64@MSOP8 [DX1015]
24LC64@SOIC8 [DX1045]
24LC64@TSSOP8 [DX1059]
24LC64F [DX0001]
24LC64F(Rotated)@TSSOP8 [DX1059]
24LC64F@DFN8 [DX4047]

24LC64F@MSOP8 [DX1015]
24LC64F@SOIC8 [DX1045]
24LC64F@TSSOP8 [DX1059]
24LC65 [DX0001]
24LC65@DFN8 [DX4047]
24LC65@SOIC8 [DX1045]
24LCS21 [DX0001]
24LCS21@SOIC8 [DX1045]
24LCS21A [DX0001]
24LCS21A@SOIC8 [DX1045]
24LCS22 [DX0001]
24LCS22@SOIC8 [DX1045]
24LCS22A [DX0001]
24LCS22A@SOIC8 [DX1045]
24LCS52 [DX0001]
24LCS52@DFN8 [DX4002]
24LCS52@MSOP8 [DX1015]
24LCS52@SOIC8 [DX1045]
24LCS52@TSSOP8 [DX1059]
24LCS61 [DX0001]
24LCS61@SOIC8 [DX1045]
24LCS62 [DX0001]
24LCS62@SOIC8 [DX1045]
24VL014 [DX0001]
24VL014@MSOP8 [DX1015]
24VL014@SOIC8 [DX1045]
24VL014@SOT-23 [DX1041]
24VL014@TDFN8 [DX4047]
24VL014@TSSOP8 [DX1059]
24VL024 [DX0001]
24VL024@MSOP8 [DX1015]
24VL024@SOIC8 [DX1045]
24VL024@TDFN8 [DX4047]
24VL024@TSSOP8 [DX1059]
24VL025 [DX0001]
24VL025@MSOP8 [DX1015]
24VL025@SOIC8 [DX1045]
24VL025@SOT-23 [DX1041]
24VL025@TDFN8 [DX4047]
24VL025@TSSOP8 [DX1059]
25A512@SOIC8 [DX1045]
25A512@TSSOP8 [DX1059]
25AA010A [DX0001]
25AA010A@DFN8 [DX4005]
25AA010A@MSOP8 [DX1044]
25AA010A@SOIC8 [DX1045]
25AA010A@SOT-23 [DX1041]
25AA010A@TSSOP8 [DX1059]
25AA010A[X-Rotated]@TSSOP8 [DX1059]
25AA020A [DX0001]
25AA020A@DFN8 [DX4005]
25AA020A@MSOP8 [DX1044]
25AA020A@SOIC8 [DX1045]
25AA020A@SOT-23 [DX1041]
25AA020A@TSSOP8 [DX1059]
25AA020A[X-Rotated]@TSSOP8 [DX1059]
25AA040 [DX0001]
25AA040@SOIC8 [DX1045]
25AA040@TSSOP8 [DX1059]
25AA040A [DX0001]
25AA040A@DFN8 [DX4005]
25AA040A@MSOP8 [DX1044]
25AA040A@SOIC8 [DX1045]
25AA040A@SOT-23 [DX1041]
25AA040A@TSSOP8 [DX1059]
25AA040A[X-Rotated]@TSSOP8 [DX1059]
25AA080 [DX0001]
25AA080@SOIC8 [DX1045]
25AA080A [DX0001]
25AA080A@MSOP8 [DX1044]
25AA080A@SOIC8 [DX1045]
25AA080A@TSSOP8 [DX1059]
25AA080B [DX0001]
25AA080B@MSOP8 [DX1044]
25AA080B@SOIC8 [DX1045]
25AA080B@TSSOP8 [DX1059]
25AA080C [DX0001]
25AA080C@MSOP8 [DX1044]
25AA080C@SOIC8 [DX1045]
25AA080C@TSSOP8 [DX1059]
25AA080D [DX0001]
25AA080D@MSOP8 [DX1044]
25AA080D@SOIC8 [DX1045]
25AA080D@TSSOP8 [DX1059]
25AA1024 [DX0001]
25AA1024@DFN8 [DX4005]
25AA1024@SOIC8 [DX1045]
25AA1024@SOIJ8 [DX1044]
25AA128 [DX0001]
25AA128@DFN8 [DX4005]
25AA128@SOIC8(4.0) [DX1045]
25AA128@SOIC8(5.4) [DX1044]

25AA128@TSSOP8 [DX1059]
25AA128[X-Rotated]@TSSOP8 [DX1059]
25AA160 [DX0001]
25AA160@SOIC8 [DX1045]
25AA160A [DX0001]
25AA160A@MSOP8 [DX1044]
25AA160A@SOIC8 [DX1045]
25AA160A@TSSOP8 [DX1059]
25AA160B [DX0001]
25AA160B@MSOP8 [DX1044]
25AA160B@SOIC8 [DX1045]
25AA160B@TSSOP8 [DX1059]
25AA160C [DX0001]
25AA160C@MSOP8 [DX1044]
25AA160C@SOIC8 [DX1045]
25AA160C@TDFN8 [DX4002]
25AA160C@TSSOP8 [DX1059]
25AA160D [DX0001]
25AA160D@MSOP8 [DX1044]
25AA160D@SOIC8 [DX1045]
25AA160D@TDFN8 [DX4002]
25AA160D@TSSOP8 [DX1059]
25AA256 [DX0001]
25AA256@DFN8 [DX4005]
25AA256@SOIC8(4.0) [DX1045]
25AA256@SOIC8(5.4) [DX1044]
25AA256@TSSOP8 [DX1059]
25AA256[X-Rotated]@TSSOP8 [DX1059]
25AA320 [DX0001]
25AA320@SOIC8 [DX1045]
25AA320@TSSOP14 [DX1000]
25AA320@TSSOP8 [DX1059]
25AA320A [DX0001]
25AA320A@DFN8 [DX4005]
25AA320A@MSOP8 [DX1044]
25AA320A@SOIC8 [DX1045]
25AA320A@TDFN8 [DX4002]
25AA320A@TSSOP8 [DX1059]
25AA320A@XTSSOP8 [DX1059]
25AA512 [DX0001]
25AA512@DFN8 [DX4005]
25AA512@SOIC8 [DX1045]
25AA512@SOIJ8 [DX1044]
25AA640 [DX0001]
25AA640@SOIC8 [DX1045]
25AA640@TSSOP8 [DX1059]
25AA640A [DX0001]
25AA640A@DFN8 [DX4005]
25AA640A@MSOP8 [DX1044]
25AA640A@SOIC8 [DX1045]
25AA640A@TDFN8 [DX4002]
25AA640A@TSSOP8 [DX1059]
25AA640A@XTSSOP8 [DX1059]
25C040 [DX0001]
25C040@SOIC8 [DX1045]
25C040@TSSOP8 [DX1059]
25C080 [DX0001]
25C080@SOIC8 [DX1045]
25C160 [DX0001]
25C160@SOIC8 [DX1045]
25C320 [DX0001]
25C320@SOIC8 [DX1045]
25C320@TSSOP14 [DX1000]
25C320@TSSOP8 [DX1059]
25C640 [DX0001]
25C640@SOIC8 [DX1045]
25C640@TSSOP8 [DX1059]
25LC010A [DX0001]
25LC010A@DFN8 [DX4005]
25LC010A@MSOP8 [DX1044]
25LC010A@SOIC8 [DX1045]
25LC010A@SOT-23 [DX1041]
25LC010A@TSSOP8 [DX1059]
25LC010A[X-Rotated]@TSSOP8 [DX1059]
25LC020A [DX0001]
25LC020A@DFN8 [DX4005]
25LC020A@MSOP8 [DX1044]
25LC020A@SOIC8 [DX1045]
25LC020A@SOT-23 [DX1041]
25LC020A@TSSOP8 [DX1059]
25LC020A[X-Rotated]@TSSOP8 [DX1059]
25LC040 [DX0001]
25LC040@SOIC8 [DX1045]
25LC040@TSSOP8
25LC040A [DX0001]
25LC040A@DFN8 [DX4005]
25LC040A@MSOP8 [DX1044]
25LC040A@SOIC8 [DX1045]
25LC040A@SOT-23 [DX1041]

25LC040A@TSSOP8 [DX1059]
25LC040A[X-Rotated]@TSSOP8 [DX1059]
25LC080 [DX0001]
25LC080@SOIC8 [DX1045]
25LC080A [DX0001]
25LC080A@MSOP8 [DX1044]
25LC080A@SOIC8 [DX1045]
25LC080A@TSSOP8 [DX1059]
25LC080B [DX0001]
25LC080B@MSOP8 [DX1044]
25LC080B@SOIC8 [DX1045]
25LC080B@TSSOP8 [DX1059]
25LC080C [DX0001]
25LC080C@MSOP8 [DX1044]
25LC080C@SOIC8 [DX1045]
25LC080C@TSSOP8 [DX1059]
25LC080D [DX0001]
25LC080D@MSOP8 [DX1044]
25LC080D@SOIC8 [DX1045]
25LC080D@TSSOP8 [DX1059]
25LC1024 [DX0001]
25LC1024@DFN8 [DX4005]
25LC1024@SOIC8 [DX1045]
25LC1024@SOIJ8 [DX1044]
25LC128 [DX0001]
25LC128@DFN8 [DX4005]
25LC128@SOIC8(4.0) [DX1045]
25LC128@SOIC8(5.4) [DX1044]
25LC128@TSSOP8 [DX1059]
25LC128[X-Rotated]@TSSOP8 [DX1059]
25LC160 [DX0001]
25LC160@SOIC8 [DX1045]
25LC160A [DX0001]
25LC160A@MSOP8 [DX1044]
25LC160A@SOIC8 [DX1045]
25LC160A@TSSOP8 [DX1059]
25LC160B [DX0001]
25LC160B@MSOP8 [DX1044]
25LC160B@SOIC8 [DX1045]
25LC160B@TSSOP8 [DX1059]
25LC160C [DX0001]
25LC160C@MSOP8 [DX1044]
25LC160C@SOIC8 [DX1045]
25LC160C@TDFN8 [DX4002]
25LC160C@TSSOP8 [DX1059]
25LC160D [DX0001]
25LC160D@MSOP8 [DX1044]
25LC160D@SOIC8 [DX1045]
25LC160D@TDFN8 [DX4002]
25LC160D@TSSOP8 [DX1059]
25LC256 [DX0001]
25LC256@DFN8 [DX4005]
25LC256@SOIC8(4.0) [DX1045]
25LC256@SOIC8(5.4) [DX1044]
25LC256@TSSOP8 [DX1059]
25LC256[X-Rotated]@TSSOP8 [DX1059]
25LC320 [DX0001]
25LC320(SN)@SOIC8 [DX1045]
25LC320@TSSOP14 [DX1000]
25LC320@TSSOP8 [DX1059]
25LC320A [DX0001]
25LC320A@DFN8 [DX4005]
25LC320A@MSOP8 [DX1044]
25LC320A@SOIC8 [DX1045]
25LC320A@TDFN8 [DX4002]
25LC320A@TSSOP8 [DX1059]
25LC320A@XTSSOP8 [DX1059]
25LC512 [DX0001]
25LC512@DFN8 [DX4005]
25LC512@SOIC8 [DX1045]
25LC512@SOIJ8 [DX1044]
25LC640 [DX0001]
25LC640@SOIC8 [DX1045]
25LC640@TSSOP8 [DX1059]
25LC640A [DX0001]
25LC640A@DFN8 [DX4005]
25LC640A@MSOP8 [DX1044]
25LC640A@SOIC8 [DX1045]
25LC640A@TDFN8 [DX4002]
25LC640A@TSSOP8 [DX1059]
25LC640A@XTSSOP8 [DX1059]
27256 [DX0001]
27256@PLCC32 [DX2032]
27C128 [DX0001]
27C128@PLCC32 [DX2032]
27C128A [DX0001]
27C128A@PLCC32 [DX2032]
27C256 [DX0001]
27C256@PLCC32 [DX2032]
27C32A [DX0001]

27C512 [DX0001]
27C512@PLCC32 [DX2032]
27C512A [DX0001]
27C512A@PLCC32 [DX2032]
27C513 [DX0001]
27C64 [DX0001]
27C64@PLCC32 [DX2032]
27C64@SOIC28 [DX1033]
27HC1616 [DX0001]
27HC1616@PLCC44 [DX2044]
27HC1616L [DX0001]
27HC1616L@PLCC44 [DX2044]
27HC191 [DX0001]
27HC191@PLCC28 [DX2028]
27HC191@SOIC24 [DX1033]
27HC256 [DX0001]
27HC256@PLCC32 [DX2032]
27HC256L [DX0001]
27HC256L@PLCC32 [DX2032]
27HC291 [DX0001]
27HC291@PLCC28 [DX2028]
27HC291@SOIC24 [DX1033]
27HC416 [DX0001]
27HC416@PLCC44 [DX2044]
27HC64 [DX0001]
27HC64@PLCC32 [DX2032]
27HC64@SOIC28 [DX1033]
27HC641 [DX0001]
27HC641@PLCC28 [DX2028]
27HC641@SOIC24 [DX1033]
27HC641L [DX0001]
27HC641L@PLCC28 [DX2028]
27HC641L@SOIC24 [DX1033]
27HC64L [DX0001]
27HC64L@PLCC32 [DX2032]
27HC64L@SOIC28 [DX1033]
27LV256 [DX0001]
27LV256@PLCC32 [DX2032]
27LV64 [DX0001]
2817 [DX0001]
2864 [DX0001]
2864@PLCC32 [DX2032]
28C04 [DX0001]
28C04@PLCC32 [DX2032]
28C04@SOIC24 [DX1033]
28C04A [DX0001]
28C04A@PLCC32 [DX2032]
28C04A@SOIC24 [DX1033]
28C04AF [DX0001]
28C04AF@PLCC32 [DX2032]
28C04AF@SOIC24 [DX1033]
28C04F [DX0001]
28C04F@PLCC32 [DX2032]
28C04F@SOIC24 [DX1033]
28C16 [DX0001]
28C16@PLCC32 [DX2032]
28C16@SOIC24 [DX1033]
28C16A [DX0001]
28C16A@PLCC32 [DX2032]
28C16A@SOIC24 [DX1033]
28C16AF [DX0001]
28C16AF@PLCC32 [DX2032]
28C16AF@SOIC24 [DX1033]
28C16F [DX0001]
28C16F@PLCC32 [DX2032]
28C16F@SOIC24 [DX1033]
28C17 [DX0001]
28C17@PLCC32 [DX2032]
28C17@SOIC28 [DX1033]
28C17A [DX0001]
28C17A@PLCC32 [DX2032]
28C17A@SOIC28 [DX1033]
28C17AF [DX0001]
28C17AF@PLCC32 [DX2032]
28C17AF@SOIC28 [DX1033]
28C17F [DX0001]
28C17F@PLCC32 [DX2032]
28C17F@SOIC28 [DX1033]
28C256 [DX0001]
28C256@PLCC32 [DX2032]
28C256F [DX0001]
28C256F@PLCC32 [DX2032]
28C64A [DX0001]
28C64A@PLCC32 [DX2032]
28C64A@SOIC28 [DX1033]
28C64A@TSOP32 [DX1002]
28C64AF [DX0001]
28C64AF@PLCC32 [DX2032]
28C64AF@SOIC28 [DX1033]
28LV64A [DX0001]
28LV64A@PLCC32 [DX2032]
28LV64A@SOIC28 [DX1033]
28PC64 [DX0001]
28PC64@PLCC32 [DX2032]
59C11 [DX0001]
59C11@SOIC8 [DX1045]

85C72 [DX0001]
85C82 [DX0001]
85C92 [DX0001]
93AA46(08bit) [DX0001]
93AA46(16bit) [DX0001]
93AA46A(08bit) [DX0001]
93AA46A(08bit)@MSOP8 [DX1015]
93AA46A(08bit)@SOT-23 [DX1041]
93AA46B(16bit) [DX0001]
93AA46B(16bit)@MSOP8 [DX1015]
93AA46B(16bit)@SOT-23 [DX1041]
93AA46C(08bit) [DX0001]
93AA46C(08bit)@MSOP8 [DX1015]
93AA46C(08bit)@TSSOP8 [DX1059]
93AA46C(16bit)@DFN8 [DX0001]
93AA46C(16bit)@SOIC8 [DX1045]
93AA56(08bit) [DX0001]
93AA56(16bit) [DX0001]
93AA56A(08bit) [DX0001]
93AA56A(08bit)@MSOP8 [DX1015]
93AA56A(08bit)@SOT-23 [DX1041]
93AA56B(16bit) [DX0001]
93AA56B(16bit)@MSOP8 [DX1015]
93AA56B(16bit)@SOT-23 [DX1041]
93AA56C(08bit) [DX0001]
93AA56C(08bit)@MSOP8 [DX1015]
93AA56C(08bit)@TSSOP8 [DX1059]
93AA56C(16bit)@DFN8 [DX0001]
93AA56C(16bit)@SOIC8 [DX1045]
93AA66(08bit) [DX0001]
93AA66(16bit) [DX0001]
93AA66A(08bit) [DX0001]
93AA66A(08bit)@MSOP8 [DX1015]
93AA66A(08bit)@SOT-23 [DX1041]
93AA66B(16bit) [DX0001]
93AA66B(16bit)@MSOP8 [DX1015]
93AA66B(16bit)@SOT-23 [DX1041]
93AA66C(08bit) [DX0001]
93AA66C(08bit)@MSOP8 [DX1015]
93AA66C(08bit)@TSSOP8 [DX1059]
93AA66C(16bit)@DFN8 [DX0001]
93AA66C(16bit)@SOIC8 [DX1045]
93AA76(08bit) [DX0001]
93AA76(16bit) [DX0001]
93AA76A(08bit) [DX0001]
93AA76A(08bit)@MSOP8 [DX1015]
93AA76A(08bit)@SOT-23 [DX1041]
93AA76B(16bit) [DX0001]
85C72@SOIC8 [DX1045]
85C82@SOIC8 [DX1045]
85C92@SOIC8 [DX1045]
93AA46(08bit)@SOIC8 [DX1045]
93AA46(16bit)@SOIC8 [DX1045]
93AA46A(08bit)@DFN8 [DX0001]
93AA46A(08bit)@SOIC8 [DX1045]
93AA46A(08bit)@TSSOP8 [DX1059]
93AA46B(16bit)@DFN8 [DX0001]
93AA46B(16bit)@SOIC8 [DX1045]
93AA46B(16bit)@TSSOP8 [DX1059]
93AA46C(08bit)@DFN8 [DX0001]
93AA46C(08bit)@SOIC8 [DX1045]
93AA46C(16bit) [DX0001]
93AA46C(16bit)@MSOP8 [DX1015]
93AA46C(16bit)@TSSOP8 [DX1059]
93AA56(08bit)@SOIC8 [DX1045]
93AA56(16bit)@SOIC8 [DX1045]
93AA56A(08bit)@DFN8 [DX0001]
93AA56A(08bit)@SOIC8 [DX1045]
93AA56A(08bit)@TSSOP8 [DX1059]
93AA56B(16bit)@DFN8 [DX0001]
93AA56B(16bit)@SOIC8 [DX1045]
93AA56B(16bit)@TSSOP8 [DX1059]
93AA56C(08bit)@DFN8 [DX0001]
93AA56C(08bit)@SOIC8 [DX1045]
93AA56C(16bit) [DX0001]
93AA56C(16bit)@MSOP8 [DX1015]
93AA56C(16bit)@TSSOP8 [DX1059]
93AA66(08bit)@SOIC8 [DX1045]
93AA66(16bit)@SOIC8 [DX1045]
93AA66A(08bit)@DFN8 [DX0001]
93AA66A(08bit)@SOIC8 [DX1045]
93AA66A(08bit)@TSSOP8 [DX1059]
93AA66B(16bit)@DFN8 [DX0001]
93AA66B(16bit)@SOIC8 [DX1045]
93AA66B(16bit)@TSSOP8 [DX1059]
93AA66C(08bit)@DFN8 [DX0001]
93AA66C(08bit)@SOIC8 [DX1045]
93AA66C(16bit) [DX0001]
93AA66C(16bit)@MSOP8 [DX1015]
93AA66C(16bit)@TSSOP8 [DX1059]
93AA76(08bit)@SOIC8 [DX1045]
93AA76(16bit)@SOIC8 [DX1045]
93AA76A(08bit)@DFN8 [DX0001]
93AA76A(08bit)@SOIC8 [DX1045]
93AA76A(08bit)@TSSOP8 [DX1059]
93AA76B(16bit)@DFN8 [DX0001]

93AA76B(16bit)@MSOP8 [DX1015]
93AA76B(16bit)@SOIC8 [DX1045]
93AA76B(16bit)@SOT-23 [DX1041]
93AA76B(16bit)@TSSOP8 [DX1059]
93AA76C(08bit) [DX0001]
93AA76C(08bit)@DFN8 [DX0001]
93AA76C(08bit)@MSOP8 [DX1015]
93AA76C(08bit)@SOIC8 [DX1045]
93AA76C(08bit)@TSSOP8 [DX1059]
93AA76C(16bit) [DX0001]
93AA76C(16bit)@DFN8 [DX0001]
93AA76C(16bit)@MSOP8 [DX1015]
93AA76C(16bit)@SOIC8 [DX1045]
93AA76C(16bit)@TSSOP8 [DX1059]
93AA86(08bit) [DX0001]
93AA86(08bit)@SOIC8 [DX1045]
93AA86(16bit) [DX0001]
93AA86(16bit)@SOIC8 [DX1045]
93AA86A(08bit) [DX0001]
93AA86A(08bit)@DFN8 [DX0001]
93AA86A(08bit)@MSOP8 [DX1015]
93AA86A(08bit)@SOIC8 [DX1045]
93AA86A(08bit)@SOT-23 [DX1041]
93AA86A(08bit)@TSSOP8 [DX1059]
93AA86B(16bit) [DX0001]
93AA86B(16bit)@DFN8 [DX0001]
93AA86B(16bit)@MSOP8 [DX1015]
93AA86B(16bit)@SOIC8 [DX1045]
93AA86B(16bit)@SOT-23 [DX1041]
93AA86B(16bit)@TSSOP8 [DX1059]
93AA86C(08bit) [DX0001]
93AA86C(08bit)@DFN8 [DX0001]
93AA86C(08bit)@MSOP8 [DX1015]
93AA86C(08bit)@SOIC8 [DX1045]
93AA86C(08bit)@TSSOP8 [DX1059]
93AA86C(16bit) [DX0001]
93AA86C(16bit)@DFN8 [DX0001]
93AA86C(16bit)@MSOP8 [DX1015]
93AA86C(16bit)@SOIC8 [DX1045]
93AA86C(16bit)@TSSOP8 [DX1059]
93C06(08bit) [DX0001]
93C06(08bit)@SOIC8 [DX1045]
93C06(16bit) [DX0001]
93C06(16bit)@SOIC8 [DX1045]
93C46(08bit) [DX0001]
93C46(08bit)@SOIC8 [DX1045]
93C46(16bit) [DX0001]
93C46(16bit)@SOIC8 [DX1045]
93C46A(08bit) [DX0001]
93C46A(08bit)@DFN8 [DX0001]
93C46A(08bit)@MSOP8 [DX1015]
93C46A(08bit)@SOIC8 [DX1045]
93C46A(08bit)@SOT-23 [DX1041]
93C46A(08bit)@TSSOP8 [DX1059]
93C46B(16bit) [DX0001]
93C46B(16bit)@DFN8 [DX0001]
93C46B(16bit)@MSOP8 [DX1015]
93C46B(16bit)@SOIC8 [DX1045]
93C46B(16bit)@SOT-23 [DX1041]
93C46B(16bit)@TSSOP8 [DX1059]
93C46C(08bit) [DX0001]
93C46C(08bit)@DFN8 [DX0001]
93C46C(08bit)@MSOP8 [DX1015]
93C46C(08bit)@SOIC8 [DX1045]
93C46C(08bit)@TSSOP8 [DX1059]
93C46C(16bit) [DX0001]
93C46C(16bit)@DFN8 [DX0001]
93C46C(16bit)@MSOP8 [DX1015]
93C46C(16bit)@SOIC8 [DX1045]
93C46C(16bit)@TSSOP8 [DX1059]
93C56(08bit) [DX0001]
93C56(08bit)@SOIC8 [DX1045]
93C56(16bit) [DX0001]
93C56(16bit)@SOIC8 [DX1045]
93C56A(08bit) [DX0001]
93C56A(08bit)@DFN8 [DX0001]
93C56A(08bit)@MSOP8 [DX1015]
93C56A(08bit)@SOIC8 [DX1045]
93C56A(08bit)@SOT-23 [DX1041]
93C56A(08bit)@TSSOP8 [DX1059]
93C56B(16bit) [DX0001]
93C56B(16bit)@DFN8 [DX0001]
93C56B(16bit)@MSOP8 [DX1015]
93C56B(16bit)@SOIC8 [DX1045]
93C56B(16bit)@SOT-23 [DX1041]
93C56B(16bit)@TSSOP8 [DX1059]
93C56C(08bit) [DX0001]
93C56C(08bit)@DFN8 [DX0001]
93C56C(08bit)@MSOP8 [DX1015]
93C56C(08bit)@SOIC8 [DX1045]
93C56C(08bit)@TSSOP8 [DX1059]
93C56C(16bit) [DX0001]
93C56C(16bit)@DFN8 [DX0001]
93C56C(16bit)@MSOP8 [DX1015]
93C56C(16bit)@SOIC8 [DX1045]
93C56C(16bit)@TSSOP8 [DX1059]

93C66(08bit) [DX0001]
93C66(16bit) [DX0001]
93C66A(08bit) [DX0001]
93C66A(08bit)@MSOP8 [DX1015]
93C66A(08bit)@SOT-23 [DX1041]
93C66B(16bit) [DX0001]
93C66B(16bit)@MSOP8 [DX1015]
93C66B(16bit)@SOT-23 [DX1041]
93C66C(08bit) [DX0001]
93C66C(08bit)@MSOP8 [DX1015]
93C66C(08bit)@TSSOP8 [DX1059]
93C66C(16bit)@DFN8 [DX0001]
93C66C(16bit)@SOIC8 [DX1045]
93C76(08bit) [DX0001]
93C76(16bit) [DX0001]
93C76A(08bit) [DX0001]
93C76A(08bit)@MSOP8 [DX1015]
93C76A(08bit)@SOT-23 [DX1041]
93C76B(16bit) [DX0001]
93C76B(16bit)@MSOP8 [DX1015]
93C76B(16bit)@SOT-23 [DX1041]
93C76C(08bit) [DX0001]
93C76C(08bit)@MSOP8 [DX1015]
93C76C(08bit)@TSSOP8 [DX1059]
93C76C(16bit)@DFN8 [DX0001]
93C76C(16bit)@SOIC8 [DX1045]
93C86(08bit) [DX0001]
93C86(16bit) [DX0001]
93C86A(08bit) [DX0001]
93C86A(08bit)@MSOP8 [DX1015]
93C86A(08bit)@SOT-23 [DX1041]
93C86B(16bit) [DX0001]
93C86B(16bit)@MSOP8 [DX1015]
93C86B(16bit)@SOT-23 [DX1041]
93C86C(08bit) [DX0001]
93C86C(08bit)@MSOP8 [DX1015]
93C86C(08bit)@TSSOP8 [DX1059]
93C86C(16bit)@DFN8 [DX0001]
93C86C(16bit)@SOIC8 [DX1045]
93LC46(08bit) [DX0001]
93LC46(16bit) [DX0001]
93LC46A(08bit) [DX0001]
93LC46A(08bit)@MSOP8 [DX1015]
93LC46A(08bit)@SOT-23 [DX1041]
93LC46A-R(08bit)@SOIC8 [DX1045]
93LC46B(16bit) [DX0001]
93LC46B(16bit)@MSOP8 [DX1015]
93LC46B(16bit)@SOT-23 [DX1041]
93C66(08bit)@SOIC8 [DX1045]
93C66(16bit)@SOIC8 [DX1045]
93C66A(08bit)@DFN8 [DX0001]
93C66A(08bit)@SOIC8 [DX1045]
93C66A(08bit)@TSSOP8 [DX1059]
93C66B(16bit)@DFN8 [DX0001]
93C66B(16bit)@SOIC8 [DX1045]
93C66B(16bit)@TSSOP8 [DX1059]
93C66C(08bit)@DFN8 [DX0001]
93C66C(08bit)@SOIC8 [DX1045]
93C66C(16bit) [DX0001]
93C66C(16bit)@MSOP8 [DX1015]
93C66C(16bit)@TSSOP8 [DX1059]
93C76(08bit)@SOIC8 [DX1045]
93C76(16bit)@SOIC8 [DX1045]
93C76A(08bit)@DFN8 [DX0001]
93C76A(08bit)@SOIC8 [DX1045]
93C76A(08bit)@TSSOP8 [DX1059]
93C76B(16bit)@DFN8 [DX0001]
93C76B(16bit)@SOIC8 [DX1045]
93C76B(16bit)@TSSOP8 [DX1059]
93C76C(08bit)@DFN8 [DX0001]
93C76C(08bit)@SOIC8 [DX1045]
93C76C(16bit) [DX0001]
93C76C(16bit)@MSOP8 [DX1015]
93C76C(16bit)@TSSOP8 [DX1059]
93C86(08bit)@SOIC8 [DX1045]
93C86(16bit)@SOIC8 [DX1045]
93C86A(08bit)@DFN8 [DX0001]
93C86A(08bit)@SOIC8 [DX1045]
93C86A(08bit)@TSSOP8 [DX1059]
93C86B(16bit)@DFN8 [DX0001]
93C86B(16bit)@SOIC8 [DX1045]
93C86B(16bit)@TSSOP8 [DX1059]
93C86C(08bit)@DFN8 [DX0001]
93C86C(08bit)@SOIC8 [DX1045]
93C86C(16bit) [DX0001]
93C86C(16bit)@MSOP8 [DX1015]
93C86C(16bit)@TSSOP8 [DX1059]
93LC46(08bit)@SOIC8 [DX1045]
93LC46(16bit)@SOIC8 [DX1045]
93LC46A(08bit)@DFN8 [DX0001]
93LC46A(08bit)@SOIC8 [DX1045]
93LC46A(08bit)@TSSOP8 [DX1059]
93LC46A-R(16bit)@SOIC8 [DX1045]
93LC46B(16bit)@DFN8 [DX0001]
93LC46B(16bit)@SOIC8 [DX1045]
93LC46B(16bit)@TSSOP8 [DX1059]

93LC46BX [DX0001]
93LC46BX@SOIC8 [DX1045]
93LC46C(08bit) [DX0001]
93LC46C(08bit)@DFN8 [DX0001]
93LC46C(08bit)@MSOP8 [DX1015]
93LC46C(08bit)@SOIC8 [DX1045]
93LC46C(08bit)@TSSOP8 [DX1059]
93LC46C(16bit) [DX0001]
93LC46C(16bit)@DFN8 [DX0001]
93LC46C(16bit)@MSOP8 [DX1015]
93LC46C(16bit)@SOIC8 [DX1045]
93LC46C(16bit)@TSSOP8 [DX1059]
93LC56(08bit) [DX0001]
93LC56(08bit)@SOIC8 [DX1045]
93LC56(16bit) [DX0001]
93LC56(16bit)@SOIC8 [DX1045]
93LC56A(08bit) [DX0001]
93LC56A(08bit)@DFN8 [DX0001]
93LC56A(08bit)@MSOP8 [DX1015]
93LC56A(08bit)@SOIC8 [DX1045]
93LC56A(08bit)@SOT-23 [DX1041]
93LC56A(08bit)@TSSOP8 [DX1059]
93LC56B(16bit) [DX0001]
93LC56B(16bit)@DFN8 [DX0001]
93LC56B(16bit)@MSOP8 [DX1015]
93LC56B(16bit)@SOIC8 [DX1045]
93LC56B(16bit)@SOT-23 [DX1041]
93LC56B(16bit)@TSSOP8 [DX1059]
93LC56BX [DX0001]
93LC56BX@SOIC8 [DX1045]
93LC56C(08bit) [DX0001]
93LC56C(08bit)@DFN8 [DX0001]
93LC56C(08bit)@MSOP8 [DX1015]
93LC56C(08bit)@SOIC8 [DX1045]
93LC56C(08bit)@TSSOP8 [DX1059]
93LC56C(16bit) [DX0001]
93LC56C(16bit)@DFN8 [DX0001]
93LC56C(16bit)@MSOP8 [DX1015]
93LC56C(16bit)@SOIC8 [DX1045]
93LC56C(16bit)@TSSOP8 [DX1059]
93LC66(08bit) [DX0001]
93LC66(08bit)@SOIC8 [DX1045]
93LC66(16bit) [DX0001]
93LC66(16bit)@SOIC8 [DX1045]
93LC66A(08bit) [DX0001]
93LC66A(08bit)@DFN8 [DX0001]
93LC66A(08bit)@MSOP8 [DX1015]
93LC66A(08bit)@SOIC8 [DX1045]
93LC66A(08bit)@SOT-23 [DX1041]
93LC66A(08bit)@TSSOP8 [DX1059]
93LC66B(16bit) [DX0001]
93LC66B(16bit)@DFN8 [DX0001]
93LC66B(16bit)@MSOP8 [DX1015]
93LC66B(16bit)@SOIC8 [DX1045]
93LC66B(16bit)@SOT-23 [DX1041]
93LC66B(16bit)@TSSOP8 [DX1059]
93LC66BX [DX0001]
93LC66BX@SOIC8 [DX1045]
93LC66C(08bit) [DX0001]
93LC66C(08bit)@DFN8 [DX0001]
93LC66C(08bit)@MSOP8 [DX1015]
93LC66C(08bit)@SOIC8 [DX1045]
93LC66C(08bit)@TSSOP8 [DX1059]
93LC66C(16bit) [DX0001]
93LC66C(16bit)@DFN8 [DX0001]
93LC66C(16bit)@MSOP8 [DX1015]
93LC66C(16bit)@SOIC8 [DX1045]
93LC66C(16bit)@TSSOP8 [DX1059]
93LC76(08bit) [DX0001]
93LC76(08bit)@SOIC8 [DX1045]
93LC76(16bit) [DX0001]
93LC76(16bit)@SOIC8 [DX1045]
93LC76A(08bit) [DX0001]
93LC76A(08bit)@DFN8 [DX0001]
93LC76A(08bit)@MSOP8 [DX1015]
93LC76A(08bit)@SOIC8 [DX1045]
93LC76A(08bit)@SOT-23 [DX1041]
93LC76A(08bit)@TSSOP8 [DX1059]
93LC76B(16bit) [DX0001]
93LC76B(16bit)@DFN8 [DX0001]
93LC76B(16bit)@MSOP8 [DX1015]
93LC76B(16bit)@SOIC8 [DX1045]
93LC76B(16bit)@SOT-23 [DX1041]
93LC76B(16bit)@TSSOP8 [DX1059]
93LC76C(08bit) [DX0001]
93LC76C(08bit)@DFN8 [DX0001]
93LC76C(08bit)@MSOP8 [DX1015]
93LC76C(08bit)@SOIC8 [DX1045]
93LC76C(08bit)@TSSOP8 [DX1059]
93LC76C(16bit) [DX0001]
93LC76C(16bit)@DFN8 [DX0001]
93LC76C(16bit)@MSOP8 [DX1015]
93LC76C(16bit)@SOIC8 [DX1045]
93LC76C(16bit)@TSSOP8 [DX1059]
93LC86(08bit) [DX0001]
93LC86(08bit)@SOIC8 [DX1045]

93LC86(16bit) [DX0001]
93LC86A(08bit) [DX0001]
93LC86A(08bit)@MSOP8 [DX1015]
93LC86A(08bit)@SOT-23 [DX1041]
93LC86B(16bit) [DX0001]
93LC86B(16bit)@MSOP8 [DX1015]
93LC86B(16bit)@SOT-23 [DX1041]
93LC86C(08bit) [DX0001]
93LC86C(08bit)@MSOP8 [DX1015]
93LC86C(08bit)@TSSOP8 [DX1059]
93LC86C(16bit)@DFN8 [DX0001]
93LC86C(16bit)@SOIC8 [DX1045]
93LCS46 [DX0001]
93LCS46@SOIC8 [DX1045]
93LCS56@SOIC14 [DX1000]
93LCS66 [DX0001]
93LCS66@SOIC8 [DX1045]
ER5911@SOIC8 [DX1045]
HCS101SN@SOIC8 [DX1045]
HCS200SN@SOIC8 [DX1045]
HCS201@SOIC8 [DX1045]
HCS300SN@SOIC8 [DX1045]
HCS301SN@SOIC8 [DX1045]
HCS320SN@SOIC8 [DX1045]
HCS360SN@SOIC8 [DX1045]
HCS361SN@SOIC8 [DX1045]
HCS362@SOIC8 [DX1045]
HCS410 [DX0001]
HCS410@TSSOP8 [DX1059]
HCS412@SOIC8 [DX1045]
HCS512@SOIC18 [DX1016]
MCP79510@TDFN10 [DX4007]
MCP79511@TDFN10 [DX4007]
MCP79512@TDFN10 [DX4007]
MCP79520@TDFN10 [DX4007]
MCP79521@TDFN10 [DX4007]
MCP79522@TDFN10 [DX4007]
MCP795B10@TSSOP14 [DX1000]
MCP795B11@TSSOP14 [DX1000]
MCP795B12@TSSOP14 [DX1000]
MCP795B20@TSSOP14 [DX1000]
MCP795B21@TSSOP14 [DX1000]
MCP795B22@TSSOP14 [DX1000]
MCP795W10@TSSOP14 [DX1000]
MCP795W11@TSSOP14 [DX1000]
MCP795W12@TSSOP14 [DX1000]
MCP795W20@TSSOP14 [DX1000]
MCP795W21@TSSOP14 [DX1000]
93LC86(16bit)@SOIC8 [DX1045]
93LC86A(08bit)@DFN8 [DX0001]
93LC86A(08bit)@SOIC8 [DX1045]
93LC86A(08bit)@TSSOP8 [DX1059]
93LC86B(16bit)@DFN8 [DX0001]
93LC86B(16bit)@SOIC8 [DX1045]
93LC86B(16bit)@TSSOP8 [DX1059]
93LC86C(08bit)@DFN8 [DX0001]
93LC86C(08bit)@SOIC8 [DX1045]
93LC86C(16bit) [DX0001]
93LC86C(16bit)@MSOP8 [DX1015]
93LC86C(16bit)@TSSOP8 [DX1059]
93LCS46@SOIC14 [DX1000]
93LCS56 [DX0001]
93LCS56@SOIC8 [DX1045]
93LCS66@SOIC14 [DX1000]
ER5911 [DX0001]
HCS101 [DX0001]
HCS200 [DX0001]
HCS201 [DX0001]
HCS300 [DX0001]
HCS301 [DX0001]
HCS320 [DX0001]
HCS360 [DX0001]
HCS361 [DX0001]
HCS362 [DX0001]
HCS362@TSSOP8 [DX1059]
HCS410@SOIC8 [DX1045]
HCS412 [DX0001]
HCS512 [DX0001]
MCP79510@MSOP10 [DX1015]
MCP79511@MSOP10 [DX1015]
MCP79512@MSOP10 [DX1015]
MCP79520@MSOP10 [DX1015]
MCP79521@MSOP10 [DX1015]
MCP79522@MSOP10 [DX1015]
MCP795B10@SOIC14 [DX1016]
MCP795B11@SOIC14 [DX1016]
MCP795B12@SOIC14 [DX1016]
MCP795B20@SOIC14 [DX1016]
MCP795B21@SOIC14 [DX1016]
MCP795B22@SOIC14 [DX1016]
MCP795W10@SOIC14 [DX1016]
MCP795W11@SOIC14 [DX1016]
MCP795W12@SOIC14 [DX1016]
MCP795W20@SOIC14 [DX1016]
MCP795W21@SOIC14 [DX1016]
MCP795W22@SOIC14 [DX1016]

MCP795W22@TSSOP14 [DX1000]
MCP98242@DFN8 [DX4002]
MCP98242@TDFN8 [DX4002]
MCP98242@TSSOP8 [DX4002]
MCP98242@UDFN8 [DX4002]
MCP98243@DFN8 [DX4002]
MCP98243@TDFN8 [DX4002]
MCP98243@TSSOP8 [DX4002]
MCP98243@UDFN8 [DX4002]
SST25PF020B@SOIC8 [DX1045#1]
SST25PF020B@USON8 [DX4002#1]
SST25PF020B@WSON8 [DX4005#1]
SST25PF040B@SOIC8[150mil] [DX1045#1]
SST25PF040B@SOIC8[200mil] [DX1044#1]
SST25PF040B@WSON8 [DX4005#1]
SST25PF080B@SOIC8[150mil] [DX1045#1]
SST25PF080B@SOIC8[200mil] [DX1044#1]
SST25PF080B@WSON8 [DX4005#1]
SST38VF6401@FBGA48 [DX5002]
SST38VF6401@TSOP48 [DX1004]
SST38VF6401B@FBGA48 [DX5002]
SST38VF6401B@TSOP48 [DX1004]
SST38VF6402@FBGA48 [DX5002]
SST38VF6402@TSOP48 [DX1004]
SST38VF6402B@FBGA48 [DX5002]
SST38VF6402B@TSOP48 [DX1004]
SST38VF6403@FBGA48 [DX5002]
SST38VF6403@TSOP48 [DX1004]
SST38VF6403B@FBGA48 [DX5002]
SST38VF6403B@TSOP48 [DX1004]
SST38VF6404@FBGA48 [DX5002]
SST38VF6404@TSOP48 [DX1004]
SST38VF6404B@FBGA48 [DX5002]
SST38VF6404B@TSOP48 [DX1004]

MICROCONTROLLER

CF745 [DX0001]
CF745@SOIC18 [DX1033]
CF745@SSOP20 [DX1026]
CF7645 [DX0001]
CF7645@SOIC18 [DX1033]
CF7665 [DX0001]
CF7665@SOIC18 [DX1033]
CF7685 [DX0001]
CF7685@SOIC18 [DX1033]
CF775 [DX0001]
CF775@SOIC28 [DX1033]
CF775@SSOP28 [DX1026]
dsPIC30F2010 [DX0001]
dsPIC30F2010(ISP) [DX0001]
dsPIC30F2010@SDIP28 [DX0032]
dsPIC30F2010@SDIP28(ISP) [DX0001]
dsPIC30F2010@SOIC28 [DX1033]
dsPIC30F2010@SOIC28(ISP) [DX0001]
dsPIC30F2011 [DX0001]
dsPIC30F2011(ISP) [DX0001]
dsPIC30F2011@QFN28 [DX4014]
dsPIC30F2011@QFN28(ISP) [DX0001]
dsPIC30F2011@SDIP18 [DX0032]
dsPIC30F2011@SDIP18(ISP) [DX0001]
dsPIC30F2011@SOIC18 [DX1033]
dsPIC30F2011@SOIC18(ISP) [DX0001]
dsPIC30F2012 [DX0001]
dsPIC30F2012(ISP) [DX0001]
dsPIC30F2012@QFN28 [DX4014]
dsPIC30F2012@QFN28(ISP) [DX0001]
dsPIC30F2012@SDIP28 [DX0032]
dsPIC30F2012@SDIP28(ISP) [DX0001]
dsPIC30F2012@SOIC28 [DX1033]
dsPIC30F2012@SOIC28(ISP) [DX0001]
dsPIC30F3010 [DX0001]
dsPIC30F3010(ISP) [DX0001]

dsPIC30F3010@QFN44 [DX4019]　　dsPIC30F3010@QFN44(ISP) [DX0001]
dsPIC30F3010@SDIP28 [DX0032]
dsPIC30F3010@SDIP28(ISP) [DX0001]
dsPIC30F3010@SOIC28 [DX1033]
dsPIC30F3010@SOIC28(ISP) [DX0001]
dsPIC30F3011 [DX0001]　　dsPIC30F3011(ISP) [DX0001]
dsPIC30F3011@QFN44 [DX4019]　　dsPIC30F3011@QFN44(ISP) [DX0001]
dsPIC30F3011@QFP44 [DX3003]　　dsPIC30F3011@QFP44(ISP) [DX0001]
dsPIC30F3012 [DX0001]　　dsPIC30F3012(ISP) [DX0001]
dsPIC30F3012@QFN44 [DX4019]　　dsPIC30F3012@QFN44(ISP) [DX0001]
dsPIC30F3012@QFP44 [DX3003]　　dsPIC30F3012@QFP44(ISP) [DX0001]
dsPIC30F3012@SDIP18 [DX0032]
dsPIC30F3012@SDIP18(ISP) [DX0001]
dsPIC30F3012@SOIC18 [DX1033]
dsPIC30F3012@SOIC18(ISP) [DX0001]
dsPIC30F3013 [DX0001]　　dsPIC30F3013(ISP) [DX0001]
dsPIC30F3013@QFN44 [DX4019]　　dsPIC30F3013@QFN44(ISP) [DX0001]
dsPIC30F3013@QFP44 [DX3003]　　dsPIC30F3013@QFP44(ISP) [DX0001]
dsPIC30F3013@SDIP28 [DX0032]
dsPIC30F3013@SDIP28(ISP) [DX0001]
dsPIC30F3013@SOIC28 [DX1033]
dsPIC30F3013@SOIC28(ISP) [DX0001]
dsPIC30F3014 [DX0001]　　dsPIC30F3014(ISP) [DX0001]
dsPIC30F3014@QFN44 [DX4019]　　dsPIC30F3014@QFN44(ISP) [DX0001]
dsPIC30F3014@QFP44 [DX3003]　　dsPIC30F3014@QFP44(ISP) [DX0001]
dsPIC30F4011 [DX0001]　　dsPIC30F4011(ISP) [DX0001]
dsPIC30F4011@QFN44 [DX4019]　　dsPIC30F4011@QFN44(ISP) [DX0001]
dsPIC30F4011@QFP44 [DX3003]
dsPIC30F4011@QFP44(Delta) [DX3003]
dsPIC30F4011@QFP44(ISP) [DX0001]　　dsPIC30F4011@QFP44(LB) [DX3003]
dsPIC30F4011@QFP44(LB)(Delta) [DX3003]
dsPIC30F4012 [DX0001]　　dsPIC30F4012(ISP) [DX0001]
dsPIC30F4012@QFN44 [DX4019]　　dsPIC30F4012@QFN44(ISP) [DX0001]
dsPIC30F4012@SDIP28 [DX0032]
dsPIC30F4012@SDIP28(ISP) [DX0001]
dsPIC30F4012@SOIC28 [DX1033]
dsPIC30F4012@SOIC28(ISP) [DX0001]
dsPIC30F4013 [DX0001]　　dsPIC30F4013(ISP) [DX0001]
dsPIC30F4013@QFN44 [DX4019]　　dsPIC30F4013@QFN44(ISP) [DX0001]
dsPIC30F4013@QFP44 [DX3003]　　dsPIC30F4013@QFP44(ISP) [DX0001]
dsPIC30F5011@QFP64 [DX3011]　　dsPIC30F5011@QFP64(ISP) [DX0001]
dsPIC30F5013@QFP80 [DX3016]　　dsPIC30F5013@QFP80(ISP) [DX0001]
dsPIC30F5015@QFP64 [DX3011]　　dsPIC30F5015@QFP64(ISP) [DX0001]
dsPIC30F5016@QFP80 [DX3016]　　dsPIC30F5016@QFP80(ISP) [DX0001]
dsPIC30F6010@QFP80(ISP) [DX0001]
dsPIC30F6010@TQFP80(ISP) [DX0001]
dsPIC30F6010@TQFP80[14*14] [DX3016]
dsPIC30F6010@TQFP80[16*16] [DX3017]

dsPIC30F6010A@QFP80(ISP) [DX0001]
dsPIC30F6010A@TQFP80(ISP) [DX0001]
dsPIC30F6010A@TQFP80[14*14] [DX3016]
dsPIC30F6010A@TQFP80[16*16] [DX3017]
dsPIC30F6011@QFP64 [DX3011]　　dsPIC30F6011@QFP64(ISP) [DX0001]
dsPIC30F6011@TQFP64 [DX3013]
dsPIC30F6011@TQFP64(ISP) [DX0001]
dsPIC30F6011A@QFP64 [DX3011]
dsPIC30F6011A@QFP64(ISP) [DX0001]
dsPIC30F6011A@TQFP64 [DX3013]
dsPIC30F6011A@TQFP64(ISP) [DX0001]
dsPIC30F6012@QFP64 [DX3011]　　dsPIC30F6012@QFP64(ISP) [DX0001]
dsPIC30F6012@TQFP64 [DX3013]
dsPIC30F6012@TQFP64(ISP) [DX0001]
dsPIC30F6012A@QFP64 [DX3011]　　dsPIC30F6012A@QFP64(ISP)
dsPIC30F6012A@TQFP64 [DX3013]　　dsPIC30F6012A@TQFP64(ISP)
dsPIC30F6013@QFP80(ISP) [DX0001]
dsPIC30F6013@TQFP80[14*14] [DX3016]
dsPIC30F6013@TQFP80[16*16] [DX3017]
dsPIC30F6013A@QFP80 [DX3016]
dsPIC30F6013A@QFP80(ISP) [DX0001]
dsPIC30F6014@QFP80(ISP) [DX0001]
dsPIC30F6014@TQFP80(ISP) [DX0001]
dsPIC30F6014@TQFP80[14*14] [DX3016]
dsPIC30F6014@TQFP80[16*16] [DX3017]
dsPIC30F6014A@QFP80(ISP)　　dsPIC30F6014A@TQFP80(ISP)
dsPIC30F6014A@TQFP80[14*14] [DX3016]
dsPIC30F6014A@TQFP80[16*16] [DX3017]
dsPIC30F6015@QFP64 [DX3011]　　dsPIC30F6015@QFP64(ISP) [DX0001]
dsPIC33EP128GP502 [DX0001]　　dsPIC33EP128GP502(ISP) [DX0001]
dsPIC33EP128GP502@QFN28 [DX4014]
dsPIC33EP128GP502@SOIC28 [DX1033]
dsPIC33EP128GP502@SSOP28 [DX1026]
dsPIC33EP128GP503(ISP) [DX0001]
dsPIC33EP128GP503@VTLA36 [DX4077]
dsPIC33EP128GP504(ISP) [DX0001]　　dsPIC33EP128GP504@QFN44 [DX4019]
dsPIC33EP128GP504@TQFP44 [DX3003#2]
dsPIC33EP128GP504@VTLA44 [DX4079]
dsPIC33EP128GP506(ISP) [DX0001]　　dsPIC33EP128GP506@QFN64 [DX4023]
dsPIC33EP128GP506@TQFP64 [DX3011]
dsPIC33EP128MC202 [DX0001]　　dsPIC33EP128MC202(ISP) [DX0001]
dsPIC33EP128MC202@QFN28 [DX4014]
dsPIC33EP128MC202@SOIC28 [DX1033]
dsPIC33EP128MC202@SSOP28 [DX1026]
dsPIC33EP128MC203(ISP) [DX0001]
dsPIC33EP128MC203@VTLA36 [DX4077]
dsPIC33EP128MC204(ISP) [DX0001]　　dsPIC33EP128MC204@QFN44 [DX4019]
dsPIC33EP128MC204@TQFP44 [DX3003#2]

dsPIC33EP128MC204@VTLA44 [DX4079]
dsPIC33EP128MC206(ISP) [DX0001]
dsPIC33EP128MC206@QFN64 [DX4023]
dsPIC33EP128MC206@TQFP64 [DX3011]
dsPIC33EP128MC502 [DX0001]
dsPIC33EP128MC502(ISP) [DX0001]
dsPIC33EP128MC502@QFN28 [DX4014]
dsPIC33EP128MC502@SOIC28 [DX1033]
dsPIC33EP128MC502@SSOP28 [DX1026]
dsPIC33EP128MC503(ISP) [DX0001]
dsPIC33EP128MC503@VTLA36 [DX4077]
dsPIC33EP128MC504(ISP) [DX0001]
dsPIC33EP128MC504@QFN44 [DX4019]
dsPIC33EP128MC504@TQFP44 [DX3003#2]
dsPIC33EP128MC504@VTLA44 [DX4079]
dsPIC33EP128MC506(ISP) [DX0001]
dsPIC33EP128MC506@QFN64 [DX4023]
dsPIC33EP128MC506@TQFP64 [DX3011]
dsPIC33EP256GP502 [DX0001]
dsPIC33EP256GP502(ISP) [DX0001]
dsPIC33EP256GP502@QFN28 [DX4014]
dsPIC33EP256GP502@SOIC28 [DX1033]
dsPIC33EP256GP502@SSOP28 [DX1026]
dsPIC33EP256GP503(ISP) [DX0001]
dsPIC33EP256GP503@VTLA36 [DX4077]
dsPIC33EP256GP504(ISP) [DX0001]
dsPIC33EP256GP504@QFN44 [DX4019]
dsPIC33EP256GP504@TQFP44 [DX3003#2]
dsPIC33EP256GP504@VTLA44 [DX4079]
dsPIC33EP256GP506(ISP) [DX0001]
dsPIC33EP256GP506@QFN64 [DX4023]
dsPIC33EP256GP506@TQFP64 [DX3011]
dsPIC33EP256MC202 [DX0001]
dsPIC33EP256MC202(ISP) [DX0001]
dsPIC33EP256MC202@QFN28 [DX4014]
dsPIC33EP256MC202@SOIC28 [DX1033]
dsPIC33EP256MC202@SSOP28 [DX1026]
dsPIC33EP256MC203(ISP) [DX0001]
dsPIC33EP256MC203@VTLA36 [DX4077]
dsPIC33EP256MC204(ISP) [DX0001]
dsPIC33EP256MC204@QFN44 [DX4019]
dsPIC33EP256MC204@TQFP44 [DX3003#2]
dsPIC33EP256MC204@VTLA44 [DX4079]
dsPIC33EP256MC206(ISP) [DX0001]
dsPIC33EP256MC206@QFN64 [DX4023]
dsPIC33EP256MC206@TQFP64 [DX3011]
dsPIC33EP256MC502 [DX0001]
dsPIC33EP256MC502(ISP) [DX0001]
dsPIC33EP256MC502@QFN28 [DX4014]
dsPIC33EP256MC502@SOIC28 [DX1033]
dsPIC33EP256MC502@SSOP28 [DX1026]
dsPIC33EP256MC503(ISP) [DX0001]
dsPIC33EP256MC503@VTLA36 [DX4077]
dsPIC33EP256MC504(ISP) [DX0001]
dsPIC33EP256MC504@QFN44 [DX4019]
dsPIC33EP256MC504@TQFP44 [DX3003#2]
dsPIC33EP256MC504@VTLA44 [DX4079]
dsPIC33EP256MC506(ISP) [DX0001]
dsPIC33EP256MC506@QFN64 [DX4023]
dsPIC33EP256MC506@TQFP64 [DX3011]
dsPIC33EP256MU806@TQFP64 [DX3011]

dsPIC33EP256MU810@TQFP100(1) [DX3071]
dsPIC33EP256MU810@TQFP100(2) [DX3021]
dsPIC33EP32GP502 [DX0001]
dsPIC33EP32GP502(ISP) [DX0001]
dsPIC33EP32GP502@QFN28 [DX4014]
dsPIC33EP32GP502@SOIC28 [DX1033]
dsPIC33EP32GP502@SSOP28 [DX1026]
dsPIC33EP32GP503(ISP) [DX0001]
dsPIC33EP32GP503@VTLA36 [DX4077]
dsPIC33EP32GP504(ISP) [DX0001]
dsPIC33EP32GP504@QFN44 [DX4019]
dsPIC33EP32GP504@TQFP44 [DX3003]
dsPIC33EP32GP504@VTLA44 [DX4078]
dsPIC33EP32MC202 [DX0001]
dsPIC33EP32MC202(ISP) [DX0001]
dsPIC33EP32MC202@QFN28 [DX4014]
dsPIC33EP32MC202@SOIC28 [DX1033]
dsPIC33EP32MC202@SSOP28 [DX1026]
dsPIC33EP32MC203(ISP) [DX0001]
dsPIC33EP32MC203@VTLA36 [DX4077]
dsPIC33EP32MC204(ISP) [DX0001]
dsPIC33EP32MC204@QFN44 [DX4019]
dsPIC33EP32MC204@TQFP44 [DX3003]
dsPIC33EP32MC204@VTLA44 [DX4078]
dsPIC33EP32MC502 [DX0001]
dsPIC33EP32MC502(ISP) [DX0001]
dsPIC33EP32MC502@QFN28 [DX4014]
dsPIC33EP32MC502@SOIC28 [DX1033]
dsPIC33EP32MC502@SSOP28 [DX1026]
dsPIC33EP32MC503(ISP) [DX0001]
dsPIC33EP32MC503@VTLA36 [DX4077]
dsPIC33EP32MC504(ISP) [DX0001]
dsPIC33EP32MC504@QFN44 [DX4019]
dsPIC33EP32MC504@TQFP44 [DX3003]
dsPIC33EP32MC504@VTLA44 [DX4078]
dsPIC33EP512GP502 [DX0001]
dsPIC33EP512GP502(ISP) [DX0001]
dsPIC33EP512GP502@QFN28 [DX4014]
dsPIC33EP512GP502@SOIC28 [DX1033]
dsPIC33EP512GP504(ISP) [DX0001]
dsPIC33EP512GP504@QFN44 [DX4019]
dsPIC33EP512GP504@TQFP44 [DX3003#2]
dsPIC33EP512GP506(ISP) [DX0001]
dsPIC33EP512GP506@QFN64 [DX4023]
dsPIC33EP512GP506@TQFP64 [DX3011]
dsPIC33EP512MC202 [DX0001]
dsPIC33EP512MC202(ISP) [DX0001]
dsPIC33EP512MC202@QFN28 [DX4014]
dsPIC33EP512MC202@SOIC28 [DX1033]
dsPIC33EP512MC204(ISP) [DX0001]
dsPIC33EP512MC204@QFN44 [DX4019]
dsPIC33EP512MC204@TQFP44 [DX3003#2]
dsPIC33EP512MC206(ISP) [DX0001]
dsPIC33EP512MC206@QFN64 [DX4023]
dsPIC33EP512MC206@TQFP64 [DX3011]
dsPIC33EP512MC502 [DX0001]
dsPIC33EP512MC502(ISP) [DX0001]
dsPIC33EP512MC502@QFN28 [DX4014]
dsPIC33EP512MC502@SOIC28 [DX1033]
dsPIC33EP512MC504(ISP) [DX0001]
dsPIC33EP512MC504@QFN44 [DX4019]
dsPIC33EP512MC504@TQFP44 [DX3003#2]
dsPIC33EP512MC506(ISP) [DX0001]
dsPIC33EP512MC506@QFN64 [DX4023]
dsPIC33EP512MC506@TQFP64 [DX3011]
dsPIC33EP512MC806@QFN64 [DX4023]
dsPIC33EP512MC806@TQFP64 [DX3011]
dsPIC33EP64GP502 [DX0001]
dsPIC33EP64GP502(ISP) [DX0001]
dsPIC33EP64GP502@QFN28 [DX4014]
dsPIC33EP64GP502@SOIC28 [DX1033]
dsPIC33EP64GP502@SSOP28 [DX1026]
dsPIC33EP64GP503(ISP) [DX0001]
dsPIC33EP64GP503@VTLA36 [DX4077]
dsPIC33EP64GP504(ISP) [DX0001]
dsPIC33EP64GP504@QFN44 [DX4019]
dsPIC33EP64GP504@TQFP44 [DX3003]
dsPIC33EP64GP506(ISP) [DX0001]
dsPIC33EP64GP506@QFN64 [DX4023]
dsPIC33EP64GP506@TQFP64 [DX3011]
dsPIC33EP64MC202 [DX0001]

dsPIC33EP64MC202(ISP) [DX0001]
dsPIC33EP64MC202@QFN28 [DX4014]
dsPIC33EP64MC202@SOIC28 [DX1033]
dsPIC33EP64MC202@SSOP28 [DX1026]
dsPIC33EP64MC203(ISP) [DX0001]
dsPIC33EP64MC203@VTLA36 [DX4077]
dsPIC33EP64MC204(ISP) [DX0001]
dsPIC33EP64MC204@QFN44 [DX4019]
dsPIC33EP64MC204@TQFP44 [DX3003]
dsPIC33EP64MC206(ISP) [DX0001]
dsPIC33EP64MC206@QFN64 [DX4023]
dsPIC33EP64MC206@TQFP64 [DX3011]
dsPIC33EP64MC502 [DX0001]
dsPIC33EP64MC502(ISP) [DX0001]
dsPIC33EP64MC502@QFN28 [DX4014]
dsPIC33EP64MC502@SOIC28 [DX1033]
dsPIC33EP64MC502@SSOP28 [DX1026]
dsPIC33EP64MC503(ISP) [DX0001]
dsPIC33EP64MC503@VTLA36 [DX4077]
dsPIC33EP64MC504(ISP) [DX0001]
dsPIC33EP64MC504@QFN44 [DX4019]
dsPIC33EP64MC504@TQFP44 [DX3003]
dsPIC33EP64MC506(ISP) [DX0001]
dsPIC33EP64MC506@QFN64 [DX4023]
dsPIC33EP64MC506@TQFP64 [DX3011]
dsPIC33FJ06GS101 [DX0001]
dsPIC33FJ06GS101(ISP) [DX0001]
dsPIC33FJ06GS101@SOIC18 [DX1033]
dsPIC33FJ06GS101@SOIC18(ISP) [DX0001]
dsPIC33FJ06GS102 [DX0001]
dsPIC33FJ06GS102(ISP) [DX0001]
dsPIC33FJ06GS102@QFN28 [DX4014]
dsPIC33FJ06GS102@QFN28(ISP) [DX0001]
dsPIC33FJ06GS102@SOIC28 [DX1033]
dsPIC33FJ06GS102@SOIC28(ISP) [DX0001]
dsPIC33FJ06GS202 [DX0001]
dsPIC33FJ06GS202(ISP) [DX0001]
dsPIC33FJ06GS202@QFN28 [DX4014]
dsPIC33FJ06GS202@QFN28(ISP) [DX0001]
dsPIC33FJ06GS202@SOIC28 [DX1033]
dsPIC33FJ06GS202@SOIC28(ISP) [DX0001]
dsPIC33FJ128GP202 [DX0001]
dsPIC33FJ128GP202(ISP) [DX0001]
dsPIC33FJ128GP202@QFN28 [DX4032]
dsPIC33FJ128GP202@SOIC28 [DX1033]
dsPIC33FJ128GP204(ISP) [DX0001]
dsPIC33FJ128GP204@QFN44 [DX4019]
dsPIC33FJ128GP204@QFN44(DELTA) [DX4019]
dsPIC33FJ128GP204@TQFP44 [DX3003]
dsPIC33FJ128GP204@TQFP44(DELTA) [DX3003]
dsPIC33FJ128GP206(ISP) [DX0001]
dsPIC33FJ128GP206@QFN64 [DX4023]
dsPIC33FJ128GP206@TQFP64 [DX3011]
dsPIC33FJ128GP206A(ISP) [DX0001]
dsPIC33FJ128GP206A@QFN64 [DX4023]
dsPIC33FJ128GP206A@TQFP64 [DX3011]
dsPIC33FJ128GP306(ISP) [DX0001]
dsPIC33FJ128GP306@QFN64 [DX4023]
dsPIC33FJ128GP306@TQFP64 [DX3011]
dsPIC33FJ128GP306A(ISP) [DX0001]
dsPIC33FJ128GP306A@QFN64 [DX4023]
dsPIC33FJ128GP306A@TQFP64 [DX3011]
dsPIC33FJ128GP310(ISP) [DX0001]
dsPIC33FJ128GP310@TQFP100(1) [DX3021]
dsPIC33FJ128GP310@TQFP100(2) [DX3071]
dsPIC33FJ128GP310A(ISP) [DX0001]
dsPIC33FJ128GP310A@TQFP100(1) [DX3021]
dsPIC33FJ128GP310A@TQFP100(2) [DX3071]

dsPIC33FJ128GP706(ISP) [DX0001]
dsPIC33FJ128GP706@QFN64 [DX4023]
dsPIC33FJ128GP706@TQFP64 [DX3011]
dsPIC33FJ128GP706A(ISP) [DX0001]
dsPIC33FJ128GP706A@QFN64 [DX4023]
dsPIC33FJ128GP706A@TQFP64 [DX3011]
dsPIC33FJ128GP708(ISP) [DX0001]
dsPIC33FJ128GP708@TQFP80 [DX3016]
dsPIC33FJ128GP708A(ISP) [DX0001]
dsPIC33FJ128GP708A@TQFP80 [DX3016]
dsPIC33FJ128GP710(ISP) [DX0001]
dsPIC33FJ128GP710@TQFP100(1) [DX3021]
dsPIC33FJ128GP710@TQFP100(2) [DX3071]
dsPIC33FJ128GP710A(ISP) [DX0001]
dsPIC33FJ128GP710A@TQFP100(1) [DX3021]
dsPIC33FJ128GP710A@TQFP100(2) [DX3071]
dsPIC33FJ128GP802 [DX0001]
dsPIC33FJ128GP802(ISP) [DX0001]
dsPIC33FJ128GP802@QFN28 [DX4032]
dsPIC33FJ128GP802@SOIC28 [DX1033]
dsPIC33FJ128GP804(ISP) [DX0001]
dsPIC33FJ128GP804@QFN44 [DX4019]
dsPIC33FJ128GP804@TQFP44 [DX3003]
dsPIC33FJ128MC202 [DX0001]
dsPIC33FJ128MC202(ISP) [DX0001]
dsPIC33FJ128MC202@QFN28 [DX4032]
dsPIC33FJ128MC202@SOIC28 [DX1033]
dsPIC33FJ128MC204(ISP) [DX0001]
dsPIC33FJ128MC204@QFN44 [DX4019]
dsPIC33FJ128MC204@TQFP44 [DX3003]
dsPIC33FJ128MC506(ISP) [DX0001]
dsPIC33FJ128MC506@QFN64 [DX4023]
dsPIC33FJ128MC506@TQFP64 [DX3011]
dsPIC33FJ128MC506A(ISP) [DX0001]
dsPIC33FJ128MC506A@QFN64 [DX4023]
dsPIC33FJ128MC506A@TQFP64 [DX3011]
dsPIC33FJ128MC510(ISP) [DX0001]
dsPIC33FJ128MC510@TQFP100(1) [DX3021]
dsPIC33FJ128MC510@TQFP100(2) [DX3071]
dsPIC33FJ128MC510A(ISP) [DX0001]
dsPIC33FJ128MC510A@TQFP100(1) [DX3021]
dsPIC33FJ128MC510A@TQFP100(2) [DX3071]
dsPIC33FJ128MC706(ISP) [DX0001]
dsPIC33FJ128MC706@QFN64 [DX4023]
dsPIC33FJ128MC706@TQFP64 [DX3011]
dsPIC33FJ128MC706A(ISP) [DX0001]
dsPIC33FJ128MC706A@QFN64 [DX4023]
dsPIC33FJ128MC706A@TQFP64 [DX3011]
dsPIC33FJ128MC708(ISP) [DX0001]
dsPIC33FJ128MC708@TQFP80 [DX3016]
dsPIC33FJ128MC708A(ISP) [DX0001]
dsPIC33FJ128MC708A@TQFP80 [DX3016]
dsPIC33FJ128MC710(ISP) [DX0001]
dsPIC33FJ128MC710@TQFP100(1) [DX3021]
dsPIC33FJ128MC710@TQFP100(2) [DX3071]

dsPIC33FJ128MC710A(ISP) [DX0001]
dsPIC33FJ128MC710A@TQFP100(1) [DX3021]
dsPIC33FJ128MC710A@TQFP100(2) [DX3071]
dsPIC33FJ128MC802 [DX0001]　　dsPIC33FJ128MC802(ISP) [DX0001]
dsPIC33FJ128MC802@QFN28 [DX4032]
dsPIC33FJ128MC802@SOIC28 [DX1033]
dsPIC33FJ128MC804(ISP) [DX0001]　　dsPIC33FJ128MC804@QFN44 [DX4019]
dsPIC33FJ128MC804@TQFP44 [DX3003]
dsPIC33FJ12GP201 [DX0001]　　dsPIC33FJ12GP201(ISP) [DX0001]
dsPIC33FJ12GP201@SOIC18 [DX1033]
dsPIC33FJ12GP201@SOIC18(ISP) [DX0001]
dsPIC33FJ12GP202 [DX0001]　　dsPIC33FJ12GP202(ISP) [DX0001]
dsPIC33FJ12GP202@QFN28 [DX4014]
dsPIC33FJ12GP202@QFN28(ISP) [DX0001]
dsPIC33FJ12GP202@SOIC28 [DX1033]
dsPIC33FJ12GP202@SOIC28(ISP) [DX0001]
dsPIC33FJ12GP202@SSOP28 [DX1026]
dsPIC33FJ12GP202@SSOP28(ISP) [DX0001]
dsPIC33FJ12MC201 [DX0001]　　dsPIC33FJ12MC201(ISP) [DX0001]
dsPIC33FJ12MC201@SOIC20 [DX1033]
dsPIC33FJ12MC201@SOIC20(ISP) [DX0001]
dsPIC33FJ12MC201@SSOP20 [DX1026]
dsPIC33FJ12MC201@SSOP20(ISP) [DX0001]
dsPIC33FJ12MC202 [DX0001]　　dsPIC33FJ12MC202(ISP) [DX0001]
dsPIC33FJ12MC202@QFN28 [DX4014]
dsPIC33FJ12MC202@QFN28(ISP) [DX0001]
dsPIC33FJ12MC202@SOIC28 [DX1033]
dsPIC33FJ12MC202@SOIC28(ISP) [DX0001]
dsPIC33FJ12MC202@SSOP28 [DX1026]
dsPIC33FJ12MC202@SSOP28(ISP) [DX0001]
dsPIC33FJ16GP101 [DX0001]　　dsPIC33FJ16GP101@SOIC18 [DX1033]
dsPIC33FJ16GP101@SSOP20 [DX1026]　　dsPIC33FJ16GP102 [DX0001]
dsPIC33FJ16GP102@QFN28 [DX4014]　　dsPIC33FJ16GP102@SOIC28 [DX1033]
dsPIC33FJ16GP102@SSOP28 [DX1026]　　dsPIC33FJ16GP102@VLTA36 [DX4077]
dsPIC33FJ16GP304@QFN44 [DX4019]
dsPIC33FJ16GP304@QFN44(ISP) [DX0001]
dsPIC33FJ16GP304@TQFP44 [DX3003]
dsPIC33FJ16GP304@TQFP44(ISP) [DX0001]
dsPIC33FJ16GS402 [DX0001]　　dsPIC33FJ16GS402(ISP) [DX0001]
dsPIC33FJ16GS402@QFN28 [DX4014]
dsPIC33FJ16GS402@QFN28(ISP) [DX0001]
dsPIC33FJ16GS402@SOIC28 [DX1033]
dsPIC33FJ16GS402@SOIC28(ISP) [DX0001]
dsPIC33FJ16GS404@QFN44 [DX4019]
dsPIC33FJ16GS404@QFN44(ISP) [DX0001]
dsPIC33FJ16GS404@TQFP44 [DX3003]
dsPIC33FJ16GS404@TQFP44(ISP) [DX0001]
dsPIC33FJ16GS404@VLAP44 [DX4019]

dsPIC33FJ16GS404@VLAP44(ISP) [DX0001]
dsPIC33FJ16GS502 [DX0001] dsPIC33FJ16GS502(ISP) [DX0001]
dsPIC33FJ16GS502@QFN28 [DX4014]
dsPIC33FJ16GS502@QFN28(ISP) [DX0001]
dsPIC33FJ16GS502@SOIC28 [DX1033]
dsPIC33FJ16GS502@SOIC28(ISP) [DX0001]
dsPIC33FJ16GS504@QFN44 [DX4019]
dsPIC33FJ16GS504@QFN44(ISP) [DX0001]
dsPIC33FJ16GS504@TQFP44 [DX3003]
dsPIC33FJ16GS504@TQFP44(ISP) [DX0001]
dsPIC33FJ16GS504@VLAP44 [DX4019]
dsPIC33FJ16GS504@VLAP44(ISP) [DX0001]
dsPIC33FJ16MC101 [DX0001] dsPIC33FJ16MC101@SOIC20 [DX1033]
dsPIC33FJ16MC101@SSOP20 [DX1026] dsPIC33FJ16MC102 [DX0001]
dsPIC33FJ16MC102@QFN28 [DX4014] dsPIC33FJ16MC102@SOIC28 [DX1033]
dsPIC33FJ16MC102@SSOP28 [DX1026] dsPIC33FJ16MC102@VLTA36 [DX4077]
dsPIC33FJ16MC304@QFN44 [DX4019]
dsPIC33FJ16MC304@QFN44(ISP) [DX0001]
dsPIC33FJ16MC304@TQFP44 [DX3003]
dsPIC33FJ16MC304@TQFP44(ISP) [DX0001]
dsPIC33FJ256GP506(ISP) [DX0001] dsPIC33FJ256GP506@QFN64 [DX4023]
dsPIC33FJ256GP506@TQFP64 [DX3011]
dsPIC33FJ256GP506A(ISP) [DX0001]
dsPIC33FJ256GP506A@QFN64 [DX4023]
dsPIC33FJ256GP506A@TQFP64 [DX3011]
dsPIC33FJ256GP510(ISP) [DX0001]
dsPIC33FJ256GP510@TQFP100(1) [DX3021]
dsPIC33FJ256GP510@TQFP100(2) [DX3071]
dsPIC33FJ256GP510A(ISP) [DX0001]
dsPIC33FJ256GP510A@TQFP100(1) [DX3021]
dsPIC33FJ256GP510A@TQFP100(2) [DX3071]
dsPIC33FJ256GP710(ISP) [DX0001]
dsPIC33FJ256GP710@TQFP100(1) [DX3021]
dsPIC33FJ256GP710@TQFP100(2) [DX3071]
dsPIC33FJ256GP710A(ISP) [DX0001]
dsPIC33FJ256GP710A@TQFP100(1) [DX3021]
dsPIC33FJ256GP710A@TQFP100(2) [DX3071]
dsPIC33FJ256MC510(ISP) [DX0001]
dsPIC33FJ256MC510@TQFP100(1) [DX3021]
dsPIC33FJ256MC510@TQFP100(2) [DX3071]
dsPIC33FJ256MC510A(ISP) [DX0001]
dsPIC33FJ256MC510A@TQFP100(1) [DX3021]
dsPIC33FJ256MC510A@TQFP100(2) [DX3071]
dsPIC33FJ256MC710(ISP) [DX0001]
dsPIC33FJ256MC710@TQFP100(1) [DX3021]
dsPIC33FJ256MC710@TQFP100(2) [DX3071]
dsPIC33FJ256MC710A(ISP) [DX0001]
dsPIC33FJ256MC710A@TQFP100(1) [DX3021]

dsPIC33FJ256MC710A@TQFP100(2) [DX3071]
dsPIC33FJ32GP101 [DX0001]
dsPIC33FJ32GP101@SOIC18 [DX1033]
dsPIC33FJ32GP101@SSOP20 [DX1026]
dsPIC33FJ32GP102 [DX0001]
dsPIC33FJ32GP102@QFN28 [DX4014]
dsPIC33FJ32GP102@SOIC28 [DX1033]
dsPIC33FJ32GP102@SSOP28 [DX1026]
dsPIC33FJ32GP102@VLTA36 [DX4077]
dsPIC33FJ32GP104@LTA44 [DX4079]
dsPIC33FJ32GP104@QFN44 [DX4019]
dsPIC33FJ32GP104@TQFP44 [DX3003]
dsPIC33FJ32GP202 [DX0001]
dsPIC33FJ32GP202(ISP) [DX0001]
dsPIC33FJ32GP202@QFN28 [DX4014]
dsPIC33FJ32GP202@QFN28(ISP) [DX0001]
dsPIC33FJ32GP202@SOIC28 [DX1033]
dsPIC33FJ32GP202@SOIC28(ISP) [DX0001]
dsPIC33FJ32GP204@QFN44 [DX4019]
dsPIC33FJ32GP204@QFN44(ISP) [DX0001]
dsPIC33FJ32GP204@TQFP44 [DX3003]
dsPIC33FJ32GP204@TQFP44(ISP) [DX0001]
dsPIC33FJ32GP302 [DX0001]
dsPIC33FJ32GP302(ISP) [DX0001]
dsPIC33FJ32GP302@QFN28 [DX4014]
dsPIC33FJ32GP302@QFN28(ISP) [DX0001]
dsPIC33FJ32GP302@SOIC28 [DX1033]
dsPIC33FJ32GP302@SOIC28(ISP) [DX0001]
dsPIC33FJ32GP304@QFN44 [DX4019]
dsPIC33FJ32GP304@QFN44(ISP) [DX0001]
dsPIC33FJ32GP304@TQFP44 [DX3003]
dsPIC33FJ32GP304@TQFP44(ISP) [DX0001]
dsPIC33FJ32GS406@QFN64 [DX4023]
dsPIC33FJ32GS406@QFN64(ISP) [DX0001]
dsPIC33FJ32GS406@TQFP64 [DX3011]
dsPIC33FJ32GS406@TQFP64(ISP) [DX0001]
dsPIC33FJ32GS606@QFN64 [DX4023]
dsPIC33FJ32GS606@QFN64(ISP) [DX0001]
dsPIC33FJ32GS606@TQFP64 [DX3011]
dsPIC33FJ32GS606@TQFP64(ISP) [DX0001]
dsPIC33FJ32GS608@TQFP80 [DX3016]
dsPIC33FJ32GS608@TQFP80(ISP) [DX0001]
dsPIC33FJ32GS610@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ32GS610@TQFP100(12*1) [DX3071]
dsPIC33FJ32GS610@TQFP100(14*1) [DX3021]
dsPIC33FJ32GS610@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ32MC101 [DX0001]
dsPIC33FJ32MC101@SOIC20 [DX1033]
dsPIC33FJ32MC101@SSOP20 [DX1026]
dsPIC33FJ32MC102@QFN28 [DX4014]
dsPIC33FJ32MC102@SOIC28 [DX1033]
dsPIC33FJ32MC102@SSOP28 [DX1026]
dsPIC33FJ32MC102@VLTA36 [DX1033]
dsPIC33FJ32MC104@LTA44 [DX4079]
dsPIC33FJ32MC104@QFN44 [DX4019]
dsPIC33FJ32MC104@TQFP44 [DX3003]
dsPIC33FJ32MC202 [DX0001]
dsPIC33FJ32MC202(ISP) [DX0001]
dsPIC33FJ32MC202@QFN28 [DX4014]
dsPIC33FJ32MC202@QFN28(ISP) [DX0001]
dsPIC33FJ32MC202@SOIC28 [DX1033]
dsPIC33FJ32MC202@SOIC28(ISP) [DX0001]

dsPIC33FJ32MC204@QFN44 [DX4019]
dsPIC33FJ32MC204@QFN44(ISP) [DX0001]
dsPIC33FJ32MC204@TQFP44 [DX3003]
dsPIC33FJ32MC204@TQFP44(ISP) [DX0001]
dsPIC33FJ32MC302 [DX0001]　　dsPIC33FJ32MC302(ISP) [DX0001]
dsPIC33FJ32MC302@QFN28 [DX4014]
dsPIC33FJ32MC302@QFN28(ISP) [DX0001]
dsPIC33FJ32MC302@SOIC28 [DX1033]
dsPIC33FJ32MC302@SOIC28(ISP) [DX0001]
dsPIC33FJ32MC304@QFN44 [DX4019]
dsPIC33FJ32MC304@QFN44(ISP) [DX0001]
dsPIC33FJ32MC304@TQFP44 [DX3003]
dsPIC33FJ32MC304@TQFP44(ISP) [DX0001]
dsPIC33FJ64GP202 [DX0001]　　dsPIC33FJ64GP202(ISP) [DX0001]
dsPIC33FJ64GP202@QFN28 [DX4014]
dsPIC33FJ64GP202@QFN28(ISP) [DX0001]
dsPIC33FJ64GP202@SOIC28 [DX1033]
dsPIC33FJ64GP202@SOIC28(ISP) [DX0001]
dsPIC33FJ64GP204@QFN44 [DX4019]
dsPIC33FJ64GP204@QFN44(ISP) [DX0001]
dsPIC33FJ64GP204@TQFP44 [DX3003]
dsPIC33FJ64GP204@TQFP44(ISP) [DX0001]
dsPIC33FJ64GP206@QFN64 [DX4023]
dsPIC33FJ64GP206@QFN64(ISP) [DX0001]
dsPIC33FJ64GP206@TQFP64 [DX3011]
dsPIC33FJ64GP206@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP206A@QFN64 [DX4023]
dsPIC33FJ64GP206A@QFN64(ISP) [DX0001]
dsPIC33FJ64GP206A@TQFP64 [DX3011]
dsPIC33FJ64GP206A@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP306@QFN64 [DX4023]
dsPIC33FJ64GP306@QFN64(ISP) [DX0001]
dsPIC33FJ64GP306@TQFP64 [DX3011]
dsPIC33FJ64GP306@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP306A@QFN64 [DX4023]
dsPIC33FJ64GP306A@QFN64(ISP) [DX0001]
dsPIC33FJ64GP306A@TQFP64 [DX3011]
dsPIC33FJ64GP306A@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP310@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ64GP310@TQFP100(12*1) [DX3071]
dsPIC33FJ64GP310@TQFP100(14*1) [DX3021]
dsPIC33FJ64GP310@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ64GP310A@TQFP100(1)ISP [DX0001]
dsPIC33FJ64GP310A@TQFP100(12*1) [DX3071]
dsPIC33FJ64GP310A@TQFP100(14*1) [DX3021]
dsPIC33FJ64GP310A@TQFP100(2)ISP [DX0001]
dsPIC33FJ64GP706@QFN64 [DX4023]
dsPIC33FJ64GP706@QFN64(ISP) [DX0001]

dsPIC33FJ64GP706@TQFP64 [DX3011]
dsPIC33FJ64GP706@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP706A@QFN64 [DX4023]
dsPIC33FJ64GP706A@QFN64(ISP) [DX0001]
dsPIC33FJ64GP706A@TQFP64 [DX3011]
dsPIC33FJ64GP706A@TQFP64(ISP) [DX0001]
dsPIC33FJ64GP708@TQFP80 [DX3016]
dsPIC33FJ64GP708@TQFP80(ISP) [DX0001]
dsPIC33FJ64GP708A@TQFP80 [DX3016]
dsPIC33FJ64GP708A@TQFP80(ISP) [DX0001]
dsPIC33FJ64GP710@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ64GP710@TQFP100(12*1) [DX3071]
dsPIC33FJ64GP710@TQFP100(14*1) [DX3021]
dsPIC33FJ64GP710@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ64GP710A@TQFP100(1)ISP [DX0001]
dsPIC33FJ64GP710A@TQFP100(12*1) [DX3071]
dsPIC33FJ64GP710A@TQFP100(14*1) [DX3021]
dsPIC33FJ64GP710A@TQFP100(2)ISP [DX0001]
dsPIC33FJ64GP802 [DX0001]　　dsPIC33FJ64GP802(ISP) [DX0001]
dsPIC33FJ64GP802@QFN28 [DX4014]
dsPIC33FJ64GP802@QFN28(ISP) [DX0001]
dsPIC33FJ64GP802@SOIC28 [DX1033]
dsPIC33FJ64GP802@SOIC28(ISP) [DX0001]
dsPIC33FJ64GP804@QFN44 [DX4019]
dsPIC33FJ64GP804@QFN44(ISP) [DX0001]
dsPIC33FJ64GP804@TQFP44 [DX3003]
dsPIC33FJ64GP804@TQFP44(ISP) [DX0001]
dsPIC33FJ64GS406@QFN64 [DX4023]
dsPIC33FJ64GS406@QFN64(ISP) [DX0001]
dsPIC33FJ64GS406@TQFP64 [DX3011]
dsPIC33FJ64GS406@TQFP64(ISP) [DX0001]
dsPIC33FJ64GS606@QFN64 [DX4023]
dsPIC33FJ64GS606@QFN64(ISP) [DX0001]
dsPIC33FJ64GS606@TQFP64 [DX3011]
dsPIC33FJ64GS606@TQFP64(ISP) [DX0001]
dsPIC33FJ64GS608@TQFP80 [DX3016]
dsPIC33FJ64GS608@TQFP80(ISP) [DX0001]
dsPIC33FJ64GS610@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ64GS610@TQFP100(12*1) [DX3071]
dsPIC33FJ64GS610@TQFP100(14*1) [DX3021]
dsPIC33FJ64GS610@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ64MC202 [DX0001]　　dsPIC33FJ64MC202(ISP) [DX0001]
dsPIC33FJ64MC202@QFN28 [DX4014]
dsPIC33FJ64MC202@QFN28(ISP) [DX0001]
dsPIC33FJ64MC202@SOIC28 [DX1033]
dsPIC33FJ64MC202@SOIC28(ISP) [DX0001]
dsPIC33FJ64MC204@QFN44 [DX4019]
dsPIC33FJ64MC204@QFN44(ISP) [DX0001]

dsPIC33FJ64MC204@TQFP44 [DX3003]
dsPIC33FJ64MC204@TQFP44(ISP) [DX0001]
dsPIC33FJ64MC506@QFN64 [DX4023]
dsPIC33FJ64MC506@QFN64(ISP) [DX0001]
dsPIC33FJ64MC506@TQFP64 [DX3011]
dsPIC33FJ64MC506@TQFP64(ISP) [DX0001]
dsPIC33FJ64MC506A@QFN64 [DX4023]
dsPIC33FJ64MC506A@QFN64(ISP) [DX0001]
dsPIC33FJ64MC506A@TQFP64 [DX3011]
dsPIC33FJ64MC506A@TQFP64(ISP) [DX0001]
dsPIC33FJ64MC508@TQFP80 [DX3016]
dsPIC33FJ64MC508@TQFP80(ISP) [DX0001]
dsPIC33FJ64MC508A@TQFP80 [DX3016]
dsPIC33FJ64MC508A@TQFP80(ISP) [DX0001]
dsPIC33FJ64MC510@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ64MC510@TQFP100(12*1) [DX3071]
dsPIC33FJ64MC510@TQFP100(14*1) [DX3021]
dsPIC33FJ64MC510@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ64MC510A@TQFP100(1)ISP [DX0001]
dsPIC33FJ64MC510A@TQFP100(12*1) [DX3071]
dsPIC33FJ64MC510A@TQFP100(14*1) [DX3021]
dsPIC33FJ64MC510A@TQFP100(2)ISP [DX0001]
dsPIC33FJ64MC706@QFN64 [DX4023]
dsPIC33FJ64MC706@QFN64(ISP) [DX0001]
dsPIC33FJ64MC706@TQFP64 [DX3011]
dsPIC33FJ64MC706@TQFP64(ISP) [DX0001]
dsPIC33FJ64MC706A@QFN64 [DX4023]
dsPIC33FJ64MC706A@QFN64(ISP) [DX0001]
dsPIC33FJ64MC706A@TQFP64 [DX3011]
dsPIC33FJ64MC706A@TQFP64(ISP) [DX0001]
dsPIC33FJ64MC710@TQFP100(1)(ISP) [DX0001]
dsPIC33FJ64MC710@TQFP100(12*1) [DX3071]
dsPIC33FJ64MC710@TQFP100(14*1) [DX3021]
dsPIC33FJ64MC710@TQFP100(2)(ISP) [DX0001]
dsPIC33FJ64MC710A@TQFP100(1)ISP [DX0001]
dsPIC33FJ64MC710A@TQFP100(12*1) [DX3071]
dsPIC33FJ64MC710A@TQFP100(14*1) [DX3021]
dsPIC33FJ64MC710A@TQFP100(2)ISP [DX0001]
dsPIC33FJ64MC802 [DX0001]　　dsPIC33FJ64MC802(ISP) [DX0001]
dsPIC33FJ64MC802@QFN28 [DX4014]
dsPIC33FJ64MC802@QFN28(ISP) [DX0001]
dsPIC33FJ64MC802@SOIC28 [DX1033]
dsPIC33FJ64MC802@SOIC28(ISP) [DX0001]
dsPIC33FJ64MC804@QFN44 [DX4019]
dsPIC33FJ64MC804@QFN44(ISP) [DX0001]
dsPIC33FJ64MC804@TQFP44 [DX3003]
dsPIC33FJ64MC804@TQFP44(ISP) [DX0001]
HA2089 [DX0001]　　HA2089@QFN16 [DX4010]

HA2089@SOIC14 [DX1065]
HA2089@TSSOP14 [DX1000]
HA2099 [DX0001]
HA2099@SOIC18 [DX1033]
HA2099@SSOP20 [DX1026]
HA3089 [DX0001]
HA3089@QFN28 [DX4014]
HA3089@SOIC28 [DX1033]
HA3089@SSOP28 [DX1026]
HA3099 [DX0001]
HA3099@QFN28 [DX4014]
HA3099@SOIC28 [DX1033]
HA3099@SSOP28 [DX1026]
MCP25020 [DX0001]
MCP25020(ISP) [DX0001]
MCP25020@SOIC14 [DX1033]
MCP25020@SOIC14(ISP) [DX0001]
MCP25020@TSSOP14 [DX1016]
MCP25020@TSSOP14(ISP) [DX0001]
MCP25025 [DX0001]
MCP25025(ISP) [DX0001]
MCP25025@SOIC14 [DX1033]
MCP25025@SOIC14(ISP) [DX0001]
MCP25025@TSSOP14 [DX1016]
MCP25025@TSSOP14(ISP) [DX0001]
MCP25050 [DX0001]
MCP25050(ISP) [DX0001]
MCP25050@SOIC14 [DX1033]
MCP25050@SOIC14(ISP) [DX0001]
MCP25050@TSSOP14 [DX1016]
MCP25050@TSSOP14(ISP) [DX0001]
MCP25055 [DX0001]
MCP25055(ISP) [DX0001]
MCP25055@SOIC14 [DX1033]
MCP25055@SOIC14(ISP) [DX0001]
MCP25055@TSSOP14 [DX1016]
MCP25055@TSSOP14(ISP) [DX0001]
MCV08A [DX0001]
MCV08A@MSOP8 [DX1015]
MCV08A@SOIC8[150mil] [DX1045]
MCV08A@SOIC8[200mil] [DX1044]
MCV14A [DX0001]
MCV14A@SOIC14 [DX1016]
MCV14A@TSSOP14 [DX1000]
MCV18A [DX0001]
MCV18A@SOIC18 [DX1033]
MCV18A@SSOP20 [DX1026]
MCV28A [DX0001]
MCV28A@SOIC28 [DX1033]
MCV28A@SSOP28 [DX1026]
PIC10F200 [DX0001]
PIC10F200(ISP) [DX0001]
PIC10F200@DFN8 [DX4002]
PIC10F200@SOT6 [DX1041]
PIC10F200@SOT6(ISP) [DX0001]
PIC10F202 [DX0001]
PIC10F202(ISP) [DX0001]
PIC10F202@DFN8 [DX4002]
PIC10F202@SOT6 [DX1041]
PIC10F202@SOT6(ISP) [DX0001]
PIC10F204 [DX0001]
PIC10F204(ISP) [DX0001]
PIC10F204@DFN8 [DX4002]
PIC10F204@SOT6 [DX1041]
PIC10F204@SOT6(ISP) [DX0001]
PIC10F206 [DX0001]
PIC10F206(ISP) [DX0001]
PIC10F206@DFN8 [DX4002]
PIC10F206@SOT6 [DX1041]
PIC10F206@SOT6(ISP) [DX0001]
PIC10F220 [DX0001]
PIC10F220(ISP) [DX0001]
PIC10F220@DFN8 [DX4002]
PIC10F220@SOT6 [DX1041]
PIC10F220@SOT6(ISP) [DX0001]
PIC10F222 [DX0001]
PIC10F222(ISP) [DX0001]
PIC10F222@DFN8 [DX4002]
PIC10F222@SOT6 [DX1041]
PIC10F222@SOT6(ISP) [DX0001]
PIC10F320 [DX0001]
PIC10F320(32 WORD PRO) [DX0001]
PIC10F320(32 WORD PRO)(ISP) [DX0001]
PIC10F320(32 WORD PRO)@DFN8 [DX4002]
PIC10F320(32 WORD PRO)@SOT-23 [DX1041]
PIC10F320(ISP) [DX0001]
PIC10F320@DFN8 [DX4002]
PIC10F320@SOT-23 [DX1041]
PIC10F322 [DX0001]
PIC10F322(32 WORD PRO) [DX0001]
PIC10F322(32 WORD PRO)(ISP) [DX0001]

PIC10F322(32 WORD PRO)@DFN8 [DX4002]
PIC10F322(32 WORD PRO)@SOT-23 [DX1041]
PIC10F322(ISP) [DX0001]
PIC10F322@DFN8 [DX4002]
PIC10F322@SOT-23 [DX1041]
PIC10LF320 [DX0001]
PIC10LF320(32 WORD PRO) [DX0001]
PIC10LF320(32 WORD PRO)(ISP) [DX0001]
PIC10LF320(32 WORD PRO)@DFN8 [DX4002]
PIC10LF320(32 WORD PRO)@SOT-23 [DX1041]
PIC10LF320(ISP) [DX0001]
PIC10LF320@DFN8 [DX4002]
PIC10LF320@SOT-23 [DX1041]
PIC10LF322 [DX0001]
PIC10LF322(32 WORD PRO) [DX0001]
PIC10LF322(32 WORD PRO)(ISP) [DX0001]
PIC10LF322(32 WORD PRO)@DFN8 [DX4002]
PIC10LF322(32 WORD PRO)@SOT-23 [DX1041]
PIC10LF322(ISP) [DX0001]
PIC10LF322@DFN8 [DX4002]
PIC10LF322@SOT-23 [DX1041]
PIC12C508 [DX0001]
PIC12C508(ISP) [DX0001]
PIC12C508@SOIC8 [DX1032]
PIC12C508@SOIC8(ISP) [DX0001]
PIC12C508A [DX0001]
PIC12C508A(ISP) [DX0001]
PIC12C508A(SM)@SOIC8 [DX1032]
PIC12C508A(SM)@SOIC8(ISP) [DX0001]
PIC12C508A(SN)@SOIC8 [DX1016]
PIC12C508A(SN)@SOIC8(ISP) [DX0001]
PIC12C509 [DX0001]
PIC12C509(ISP) [DX0001]
PIC12C509(SM)@SOIC8 [DX1032]
PIC12C509(SM)@SOIC8(ISP) [DX0001]
PIC12C509(SN)@SOIC8 [DX1016]
PIC12C509(SN)@SOIC8(ISP) [DX0001]
PIC12C509A [DX0001]
PIC12C509A(ISP) [DX0001]
PIC12C509A(SM)@SOIC8 [DX1032]
PIC12C509A(SM)@SOIC8(ISP) [DX0001]
PIC12C509A(SN)@SOIC8 [DX1016]
PIC12C509A(SN)@SOIC8(ISP) [DX0001]
PIC12C509A@DFN8 [DX4005]
PIC12C509A@DFN8(ISP) [DX0001]
PIC12C671 [DX0001]
PIC12C671(ISP) [DX0001]
PIC12C671@DFN8 [DX4005]
PIC12C671@DFN8(ISP) [DX0001]
PIC12C671@SOIC8 [DX1044]
PIC12C671@SOIC8(ISP) [DX0001]
PIC12C672 [DX0001]
PIC12C672(ISP) [DX0001]
PIC12C672@DFN8 [DX4005]
PIC12C672@DFN8(ISP) [DX0001]
PIC12C672@SOIC8 [DX1044]
PIC12C672@SOIC8(ISP) [DX0001]
PIC12CE518 [DX0001]
PIC12CE518(ISP) [DX0001]
PIC12CE518@SOIC8 [DX1032]
PIC12CE518@SOIC8(ISP) [DX0001]
PIC12CE519 [DX0001]
PIC12CE519(ISP) [DX0001]
PIC12CE519(SM)@SOIC8 [DX1032]
PIC12CE519(SM)@SOIC8(ISP) [DX0001]
PIC12CE519(SN)@SOIC8 [DX1016]
PIC12CE519(SN)@SOIC8(ISP) [DX0001]
PIC12CE673 [DX0001]
PIC12CE673(ISP) [DX0001]
PIC12CE673@SOIC8 [DX1044]
PIC12CE673@SOIC8(ISP) [DX0001]

PIC12CE674 [DX0001]
PIC12CE674(ISP) [DX0001]
PIC12CE674@SOIC8 [DX1044]
PIC12CE674@SOIC8(ISP) [DX0001]
PIC12F1501 [DX0001]
PIC12F1501(ISP) [DX0001]
PIC12F1501(MC)@DFN8 [DX4002]
PIC12F1501(MF)@DFN8 [DX4003]
PIC12F1501@DFN8(ISP) [DX0001]
PIC12F1501@MSOP8 [DX1015]
PIC12F1501@MSOP8(ISP) [DX0001]
PIC12F1501@SOIC8 [DX1045]
PIC12F1501@SOIC8(ISP) [DX0001]
PIC12F1571 [DX0001]
PIC12F1571(32 word) [DX0001]
PIC12F1571(32 word)@DFN8 [DX4003]
PIC12F1571(32 word)@MSOP8 [DX1015]
PIC12F1571(32 word)@SOIC8 [DX1045]
PIC12F1571@DFN8 [DX4003]
PIC12F1571@ISP [DX0001]
PIC12F1571@MSOP8 [DX1015]
PIC12F1571@SOIC8 [DX1045]
PIC12F1572 [DX0001]
PIC12F1572(32 word) [DX0001]
PIC12F1572(32 word)@DFN8 [DX4003]
PIC12F1572(32 word)@MSOP8 [DX1015]
PIC12F1572(32 word)@SOIC8 [DX1045]
PIC12F1572@DFN8 [DX4003]
PIC12F1572@ISP [DX0001]
PIC12F1572@MSOP8 [DX1015]
PIC12F1572@SOIC8 [DX1045]
PIC12F1822 [DX0001]
PIC12F1822(8-word) [DX0001]
PIC12F1822(ISP)(HV) [DX0001]
PIC12F1822(LV) [DX0001]
PIC12F1822(LVISP) [DX0001]
PIC12F1822@DFN8 [DX4003]
PIC12F1822@DFN8(8-word) [DX4003]
PIC12F1822@DFN8(ISP)(HV) [DX0001]
PIC12F1822@DFN8(LV) [DX4002]
PIC12F1822@SOIC8 [DX1045]
PIC12F1822@SOIC8(8-word) [DX1045]
PIC12F1822@SOIC8(ISP)(HV) [DX0001]
PIC12F1822@SOIC8(LV) [DX1045]
PIC12F1840 [DX0001]
PIC12F1840(ISP)(HV) [DX0001]
PIC12F1840@DFN8 [DX4003]
PIC12F1840@DFN8(ISP)(HV) [DX0001]
PIC12F1840@SOIC8 [DX1045]
PIC12F1840@SOIC8(ISP)(HV) [DX0001]
PIC12F1840E [DX0001]
PIC12F1840E@DFN8 [DX4003]
PIC12F1840E@SOIC8 [DX1045]
PIC12F508 [DX0001]
PIC12F508(ISP) [DX0001]
PIC12F508@MSOP8 [DX1015]
PIC12F508@MSOP8(ISP) [DX0001]
PIC12F508@SOIC8 [DX1016]
PIC12F508@SOIC8(ISP) [DX0001]
PIC12F509 [DX0001]
PIC12F509(ISP) [DX0001]
PIC12F509@MSOP8 [DX1015]
PIC12F509@MSOP8(ISP) [DX0001]
PIC12F509@SOIC8 [DX1016]
PIC12F509@SOIC8(ISP) [DX0001]
PIC12F510 [DX0001]
PIC12F510(ISP) [DX0001]
PIC12F510@MSOP8 [DX1015]
PIC12F510@MSOP8(ISP) [DX0001]
PIC12F510@SOIC8(150mil) [DX1045]
PIC12F510@SOIC8(150mil)(ISP) [DX0001]
PIC12F510@SOIC8(200mil) [DX1044]
PIC12F510@SOIC8(200mil)(ISP) [DX0001]
PIC12F519 [DX0001]
PIC12F519(ISP) [DX0001]
PIC12F519@DFN8 [DX4002]
PIC12F519@DFN8(ISP) [DX0001]
PIC12F519@MSOP8 [DX1015]
PIC12F519@MSOP8(ISP) [DX0001]

PIC12F519@SOIC8 [DX1045]
PIC12F519@SOIC8(ISP) [DX0001]
PIC12F529T39A [DX1000]
PIC12F529T39A(ISP) [DX0001]
PIC12F529T48A [DX1000]
PIC12F529T48A(ISP) [DX0001]
PIC12F609 [DX0001]
PIC12F609(ISP) [DX0001]
PIC12F609@DFN8 [DX4003]
PIC12F609@DFN8(ISP) [DX0001]
PIC12F609@DFN8-S [DX4005]
PIC12F609@DFN8-S(ISP) [DX0001]
PIC12F609@MSOP8 [DX1015]
PIC12F609@MSOP8(ISP) [DX0001]
PIC12F609@SOIC8 [DX1045]
PIC12F609@SOIC8(ISP) [DX0001]
PIC12F615 [DX0001]
PIC12F615(ISP) [DX0001]
PIC12F615@DFN8 [DX4003]
PIC12F615@DFN8(ISP) [DX0001]
PIC12F615@DFN8-S [DX4005]
PIC12F615@DFN8-S(ISP) [DX0001]
PIC12F615@MSOP8 [DX1015]
PIC12F615@MSOP8(ISP) [DX0001]
PIC12F615@SOIC8 [DX1045]
PIC12F615@SOIC8(ISP) [DX0001]
PIC12F617 [DX0001]
PIC12F617(ISP) [DX0001]
PIC12F617@DFN8 [DX4003]
PIC12F617@DFN8(ISP) [DX0001]
PIC12F617@DFN8-S [DX4005]
PIC12F617@DFN8-S(ISP) [DX0001]
PIC12F617@MSOP8 [DX1015]
PIC12F617@MSOP8(ISP) [DX0001]
PIC12F617@SOIC8 [DX1045]
PIC12F617@SOIC8(ISP) [DX0001]
PIC12F629 [DX0001]
PIC12F629(ISP) [DX0001]
PIC12F629(SM)@SOIC8 [DX1032]
PIC12F629(SM)@SOIC8(ISP) [DX0001]
PIC12F629(SN)@SOIC8 [DX1016]
PIC12F629(SN)@SOIC8(ISP) [DX0001]
PIC12F629@DFN8 [DX4005]
PIC12F629@DFN8(ISP) [DX0001]
PIC12F635 [DX0001]
PIC12F635(4-WORD PRO) [DX0001]
PIC12F635(ISP) [DX0001]
PIC12F635(MD)@DFN8 [DX4004]
PIC12F635(MD)@DFN8(4-WORD PRO) [DX4004]
PIC12F635(MD)@DFN8(ISP) [DX0001]
PIC12F635(MF)@DFN8 [DX4005]
PIC12F635(MF)@DFN8(4-WORD PRO) [DX4005]
PIC12F635(MF)@DFN8(ISP) [DX0001]
PIC12F635(SM)@SOIC8 [DX1032]
PIC12F635(SM)@SOIC8(4-WORD PRO) [DX1032]
PIC12F635(SM)@SOIC8(ISP) [DX0001]
PIC12F635(SN)@SOIC8 [DX1016]
PIC12F635(SN)@SOIC8(4-WORD PRO) [DX1016]
PIC12F635(SN)@SOIC8(ISP) [DX0001]
PIC12F675 [DX0001]
PIC12F675(ISP) [DX0001]
PIC12F675(SM)@SOIC8 [DX1032]
PIC12F675(SM)@SOIC8(ISP) [DX0001]
PIC12F675(SN)@SOIC8 [DX1016]
PIC12F675(SN)@SOIC8(ISP) [DX0001]
PIC12F675@DFN8 [DX4005]
PIC12F675@DFN8(ISP) [DX0001]
PIC12F675@SSOP20 [DX1026]
PIC12F675@SSOP20(ISP) [DX0001]
PIC12F683 [DX0001]
PIC12F683(4-WORD PRO) [DX0001]
PIC12F683(ISP) [DX0001]
PIC12F683(MD)@DFN8 [DX4004]
PIC12F683(MD)@DFN8(4-WORD PRO) [DX4004]
PIC12F683(MD)@DFN8(ISP) [DX0001]
PIC12F683(MF)@DFN8 [DX4005]
PIC12F683(MF)@DFN8(4-WORD PRO) [DX4005]
PIC12F683(MF)@DFN8(ISP) [DX0001]
PIC12F683(SM)@SOIC8 [DX1032]

PIC12F683(SM)@SOIC8(4-WORD PRO) [DX1032]
PIC12F683(SM)@SOIC8(ISP) [DX0001]
PIC12F683(SN)@SOIC8 [DX1016]
PIC12F683(SN)@SOIC8(4-WORD PRO) [DX1016]
PIC12F683(SN)@SOIC8(ISP) [DX0001]
PIC12F752 [DX0001]
PIC12F752(ISP) [DX0001]
PIC12F752@DFN8 [DX4003]
PIC12F752@DFN8-S [DX4005]
PIC12F752@MSOP8 [DX1015]
PIC12F752@SOIC8 [DX1045]
PIC12HV609 [DX0001]
PIC12HV609(ISP) [DX0001]
PIC12HV609@DFN8 [DX4003]
PIC12HV609@DFN8(ISP) [DX0001]
PIC12HV609@DFN8-S [DX4005]
PIC12HV609@DFN8-S(ISP) [DX0001]
PIC12HV609@MSOP8 [DX1015]
PIC12HV609@MSOP8(ISP) [DX0001]
PIC12HV609@SOIC8 [DX1045]
PIC12HV609@SOIC8(ISP) [DX0001]
PIC12HV615 [DX0001]
PIC12HV615(ISP) [DX0001]
PIC12HV615@DFN8 [DX4003]
PIC12HV615@DFN8(ISP) [DX0001]
PIC12HV615@DFN8-S [DX4005]
PIC12HV615@DFN8-S(ISP) [DX0001]
PIC12HV615@MSOP8 [DX1015]
PIC12HV615@MSOP8(ISP) [DX0001]
PIC12HV615@SOIC8 [DX1045]
PIC12HV615@SOIC8(ISP) [DX0001]
PIC12HV752 [DX0001]
PIC12HV752(ISP) [DX0001]
PIC12HV752@DFN8 [DX4003]
PIC12HV752@DFN8-S [DX4005]
PIC12HV752@MSOP8 [DX1015]
PIC12HV752@SOIC8 [DX1045]
PIC12LC508 [DX0001]
PIC12LC508(ISP) [DX0001]
PIC12LC508@SOIC8 [DX1032]
PIC12LC508@SOIC8(ISP) [DX0001]
PIC12LC508A [DX0001]
PIC12LC508A(ISP) [DX0001]
PIC12LC508A(SM)@SOIC8 [DX1032]
PIC12LC508A(SM)@SOIC8(ISP) [DX0001]
PIC12LC508A(SN)@SOIC8 [DX1016]
PIC12LC508A(SN)@SOIC8(ISP) [DX0001]
PIC12LC509 [DX0001]
PIC12LC509(ISP) [DX0001]
PIC12LC509(SM)@SOIC8 [DX1032]
PIC12LC509(SM)@SOIC8(ISP) [DX0001]
PIC12LC509(SN)@SOIC8 [DX1016]
PIC12LC509(SN)@SOIC8(ISP) [DX0001]
PIC12LC509A [DX0001]
PIC12LC509A(ISP) [DX0001]
PIC12LC509A(SM)@SOIC8 [DX1032]
PIC12LC509A(SM)@SOIC8(ISP) [DX0001]
PIC12LC509A(SN)@SOIC8 [DX1016]
PIC12LC509A(SN)@SOIC8(ISP) [DX0001]
PIC12LC671 [DX0001]
PIC12LC671(ISP) [DX0001]
PIC12LC671@DFN8 [DX4005]
PIC12LC671@DFN8(ISP) [DX0001]
PIC12LC671@SOIC8 [DX1044]
PIC12LC671@SOIC8(ISP) [DX0001]
PIC12LC672 [DX0001]
PIC12LC672(ISP) [DX0001]
PIC12LC672@DFN8 [DX4005]
PIC12LC672@DFN8(ISP) [DX0001]
PIC12LC672@SOIC8 [DX1044]
PIC12LC672@SOIC8(ISP) [DX0001]
PIC12LF1501 [DX0001]
PIC12LF1501(ISP) [DX0001]
PIC12LF1501(MC)@DFN8 [DX4002]
PIC12LF1501(MF)@DFN8 [DX4003]
PIC12LF1501@DFN8(ISP) [DX0001]
PIC12LF1501@MSOP8 [DX1015]
PIC12LF1501@MSOP8(ISP) [DX0001]
PIC12LF1501@SOIC8 [DX1045]

PIC12LF1501@SOIC8(ISP) [DX0001]
PIC12LF1552 [DX0001]
PIC12LF1552(MC)@DFN8 [DX4002]
PIC12LF1552(MF)@DFN8 [DX4003]
PIC12LF1552@ISP [DX0001]
PIC12LF1552@MSOP8 [DX1015]
PIC12LF1552@SOIC8 [DX1045]
PIC12LF1571 [DX0001]
PIC12LF1571(32 word) [DX0001]
PIC12LF1571(32 word)@DFN8 [DX4003]
PIC12LF1571(32 word)@MSOP8 [DX1015]
PIC12LF1571(32 word)@SOIC8 [DX1045]
PIC12LF1571@DFN8 [DX4003]
PIC12LF1571@ISP [DX0001]
PIC12LF1571@MSOP8 [DX1015]
PIC12LF1571@SOIC8 [DX1045]
PIC12LF1572 [DX0001]
PIC12LF1572(32 word) [DX0001]
PIC12LF1572(32 word)@DFN8 [DX4003]
PIC12LF1572(32 word)@MSOP8 [DX1015]
PIC12LF1572(32 word)@SOIC8 [DX1045]
PIC12LF1572@DFN8 [DX4003]
PIC12LF1572@ISP [DX0001]
PIC12LF1572@MSOP8 [DX1015]
PIC12LF1572@SOIC8 [DX1045]
PIC12LF1822 [DX0001]
PIC12LF1822(8-word) [DX0001]
PIC12LF1822(ISP)(HV) [DX0001]
PIC12LF1822(LV) [DX0001]
PIC12LF1822(LVISP) [DX0001]
PIC12LF1822@DFN8 [DX4003]
PIC12LF1822@DFN8(8-word) [DX4003]
PIC12LF1822@DFN8(ISP)(HV) [DX0001]
PIC12LF1822@DFN8(LV) [DX4002]
PIC12LF1822@SOIC8 [DX1045]
PIC12LF1822@SOIC8(8-word) [DX1045]
PIC12LF1822@SOIC8(ISP)(HV) [DX0001]
PIC12LF1822@SOIC8(LV) [DX1045]
PIC12LF1840 [DX0001]
PIC12LF1840(ISP)(HV) [DX0001]
PIC12LF1840@DFN8 [DX4003]
PIC12LF1840@DFN8(ISP)(HV) [DX0001]
PIC12LF1840@SOIC8 [DX1045]
PIC12LF1840@SOIC8(ISP)(HV) [DX0001]
PIC12LF1840E [DX0001]
PIC12LF1840E@DFN8 [DX4003]
PIC12LF1840E@SOIC8 [DX1045]
PIC12LF1840T48A [DX1000]
PIC12LF508 [DX0001]
PIC12LF508(ISP) [DX0001]
PIC12LF508@MSOP8 [DX1015]
PIC12LF508@MSOP8(ISP) [DX0001]
PIC12LF508@SOIC8 [DX1016]
PIC12LF508@SOIC8(ISP) [DX0001]
PIC12LF509 [DX0001]
PIC12LF509(ISP) [DX0001]
PIC12LF509@MSOP8 [DX1015]
PIC12LF509@MSOP8(ISP) [DX0001]
PIC12LF509@SOIC8 [DX1016]
PIC12LF509@SOIC8(ISP) [DX0001]
PIC12LF519 [DX0001]
PIC12LF519(ISP) [DX0001]
PIC12LF519@DFN8 [DX4002]
PIC12LF519@DFN8(ISP) [DX0001]
PIC12LF519@MSOP8 [DX1015]
PIC12LF519@MSOP8(ISP) [DX0001]
PIC12LF519@SOIC8 [DX1045]
PIC12LF519@SOIC8(ISP) [DX0001]
PIC14000 [DX0001]
PIC14000(ISP) [DX0001]
PIC14000@SOIC28 [DX1033]
PIC14000@SOIC28(ISP) [DX0001]
PIC14000@SSOP28 [DX1026]
PIC14000@SSOP28(ISP) [DX0001]
PIC16C432 [DX0001]
PIC16C432(ISP) [DX0001]
PIC16C432@SSOP20 [DX1026]
PIC16C432@SSOP20(ISP) [DX0001]
PIC16C433 [DX0001]
PIC16C433(ISP) [DX0001]
PIC16C433@SOIC18 [DX1033]
PIC16C433@SOIC18(ISP) [DX0001]

PIC16C505 [DX0001]
PIC16C505@SOIC14 [DX1016]
PIC16C52 [DX0001]
PIC16C52@SOIC18 [DX1033]
PIC16C54 [DX0001]
PIC16C54@SOIC18 [DX1033]
PIC16C54A [DX0001]
PIC16C54A@SOIC18 [DX1033]
PIC16C54A@SSOP20 [DX1026]
PIC16C54B [DX0001]
PIC16C54B@SOIC18 [DX1033]
PIC16C54B@SSOP20 [DX1026]
PIC16C54C [DX0001]
PIC16C54C@SOIC18 [DX1033]
PIC16C54C@SSOP20 [DX1026]
PIC16C55 [DX0001]
PIC16C55@SOIC28 [DX1033]
PIC16C554 [DX0001]
PIC16C554(ISP) [DX0001]
PIC16C554@SOIC18 [DX1033]
PIC16C554@SOIC18(ISP) [DX0001]
PIC16C554@SSOP20 [DX1026]
PIC16C554@SSOP20(ISP) [DX0001]
PIC16C556 [DX0001]
PIC16C556(ISP) [DX0001]
PIC16C556@SOIC18 [DX1033]
PIC16C556@SOIC18(ISP) [DX0001]
PIC16C558 [DX0001]
PIC16C558(ISP) [DX0001]
PIC16C558@SOIC18 [DX1033]
PIC16C558@SOIC18(ISP) [DX0001]
PIC16C558@SSOP20 [DX1026]
PIC16C558@SSOP20(ISP) [DX0001]
PIC16C55A [DX0001]
PIC16C55A@SOIC28 [DX1033]
PIC16C55A@SSOP28 [DX1026]
PIC16C56 [DX0001]
PIC16C56@SOIC18 [DX1033]
PIC16C56A [DX0001]
PIC16C56A@SOIC18 [DX1033]
PIC16C56A@SSOP20 [DX1026]
PIC16C57 [DX0001]
PIC16C57@SOIC28 [DX1033]
PIC16C57@SSOP28 [DX1026]
PIC16C57C [DX0001]
PIC16C57C@SOIC28 [DX1033]
PIC16C57C@SSOP28 [DX1026]
PIC16C58 [DX0001]
PIC16C58@SOIC18 [DX1033]
PIC16C58A [DX0001]
PIC16C58A@SOIC18 [DX1033]
PIC16C58A@SSOP20 [DX1026]
PIC16C58B [DX0001]
PIC16C58B@SOIC18 [DX1033]
PIC16C58B@SSOP20 [DX1026]
PIC16C61 [DX0001]
PIC16C61(ISP) [DX0001]
PIC16C61@SOIC18 [DX1033]
PIC16C61@SOIC18(ISP) [DX0001]
PIC16C62 [DX0001]
PIC16C62(ISP) [DX0001]
PIC16C62@SOIC28 [DX1033]
PIC16C62@SOIC28(ISP) [DX0001]
PIC16C62@SSOP28 [DX1026]
PIC16C62@SSOP28(ISP) [DX0001]
PIC16C620 [DX0001]
PIC16C620(ISP) [DX0001]
PIC16C620@SOIC18 [DX1033]
PIC16C620@SOIC18(ISP) [DX0001]
PIC16C620A [DX0001]
PIC16C620A(ISP) [DX0001]
PIC16C620A@SOIC18 [DX1033]
PIC16C620A@SOIC18(ISP) [DX0001]
PIC16C620A@SSOP20 [DX1026]
PIC16C620A@SSOP20(ISP) [DX0001]
PIC16C621 [DX0001]
PIC16C621(ISP) [DX0001]
PIC16C621@SOIC18 [DX1033]
PIC16C621@SOIC18(ISP) [DX0001]
PIC16C621A [DX0001]
PIC16C621A(ISP) [DX0001]
PIC16C621A@SOIC18 [DX1033]
PIC16C621A@SOIC18(ISP) [DX0001]
PIC16C621A@SSOP20 [DX1026]
PIC16C621A@SSOP20(ISP) [DX0001]
PIC16C622 [DX0001]
PIC16C622(ISP) [DX0001]
PIC16C622@SOIC18 [DX1033]
PIC16C622@SOIC18(ISP) [DX0001]
PIC16C622A [DX0001]
PIC16C622A(ISP) [DX0001]
PIC16C622A@SOIC18 [DX1033]
PIC16C622A@SOIC18(ISP) [DX0001]
PIC16C622A@SSOP20 [DX1026]
PIC16C622A@SSOP20(ISP) [DX0001]
PIC16C625 [DX0001]

PIC16C625(ISP) [DX0001]
PIC16C625@SOIC18 [DX1033]
PIC16C625@SOIC18(ISP) [DX0001]
PIC16C62A [DX0001]
PIC16C62A(ISP) [DX0001]
PIC16C62A@SOIC28 [DX1033]
PIC16C62A@SOIC28(ISP) [DX0001]
PIC16C62A@SSOP28 [DX1026]
PIC16C62A@SSOP28(ISP) [DX0001]
PIC16C62B [DX0001]
PIC16C62B(ISP) [DX0001]
PIC16C62B@SOIC28 [DX1033]
PIC16C62B@SOIC28(ISP) [DX0001]
PIC16C62B@SSOP28 [DX1026]
PIC16C62B@SSOP28(ISP) [DX0001]
PIC16C63 [DX0001]
PIC16C63(ISP) [DX0001]
PIC16C63@SOIC28 [DX1033]
PIC16C63@SOIC28(ISP) [DX0001]
PIC16C63A [DX0001]
PIC16C63A(ISP) [DX0001]
PIC16C63A@SOIC28 [DX1033]
PIC16C63A@SOIC28(ISP) [DX0001]
PIC16C63A@SSOP28 [DX1026]
PIC16C63A@SSOP28(ISP) [DX0001]
PIC16C64 [DX0001]
PIC16C64(ISP) [DX0001]
PIC16C64@PLCC44 [DX2044]
PIC16C64@PLCC44(ISP) [DX0001]
PIC16C64@TQFP44 [DX3003]
PIC16C64@TQFP44(ISP) [DX0001]
PIC16C641 [DX0001]
PIC16C641@SOIC28 [DX1033]
PIC16C641@SSOP28 [DX1026]
PIC16C642 [DX0001]
PIC16C642@SOIC28 [DX1033]
PIC16C642@SSOP28 [DX1026]
PIC16C64A [DX0001]
PIC16C64A(ISP) [DX0001]
PIC16C64A@PLCC44 [DX2044]
PIC16C64A@PLCC44(ISP) [DX0001]
PIC16C64A@TQFP44 [DX3003]
PIC16C64A@TQFP44(ISP) [DX0001]
PIC16C65 [DX0001]
PIC16C65(ISP) [DX0001]
PIC16C65@PLCC44 [DX2044]
PIC16C65@PLCC44(ISP) [DX0001]
PIC16C65@TQFP44 [DX3003]
PIC16C65@TQFP44(ISP) [DX0001]
PIC16C65A [DX0001]
PIC16C65A(ISP) [DX0001]
PIC16C65A@PLCC44 [DX2044]
PIC16C65A@PLCC44(ISP) [DX0001]
PIC16C65A@TQFP44 [DX3003]
PIC16C65A@TQFP44(ISP) [DX0001]
PIC16C65B [DX0001]
PIC16C65B(ISP) [DX0001]
PIC16C65B@PLCC44 [DX2044]
PIC16C65B@PLCC44(ISP) [DX0001]
PIC16C65B@TQFP44 [DX3003]
PIC16C65B@TQFP44(ISP) [DX0001]
PIC16C66 [DX0001]
PIC16C66(ISP) [DX0001]
PIC16C66@SOIC28 [DX1033]
PIC16C66@SOIC28(ISP) [DX0001]
PIC16C661 [DX0001]
PIC16C661@PLCC44 [DX2044]
PIC16C661@TQFP44 [DX3003]
PIC16C662 [DX0001]
PIC16C662@PLCC44 [DX2044]
PIC16C662@TQFP44 [DX3003]
PIC16C67 [DX0001]
PIC16C67(ISP) [DX0001]
PIC16C67@PLCC44 [DX2044]
PIC16C67@PLCC44(ISP) [DX0001]
PIC16C67@TQFP44 [DX3003]
PIC16C67@TQFP44(ISP) [DX0001]
PIC16C70 [DX0001]
PIC16C70(ISP) [DX0001]
PIC16C70@SOIC18 [DX1033]
PIC16C70@SOIC18(ISP) [DX0001]
PIC16C71 [DX0001]
PIC16C71(ISP) [DX0001]
PIC16C71@SOIC18 [DX1033]
PIC16C71@SOIC18(ISP) [DX0001]
PIC16C710 [DX0001]
PIC16C710(ISP) [DX0001]
PIC16C710@SOIC18 [DX1033]
PIC16C710@SOIC18(ISP) [DX0001]
PIC16C710@SSOP20 [DX1026]
PIC16C710@SSOP20(ISP) [DX0001]
PIC16C711 [DX0001]
PIC16C711(ISP) [DX0001]
PIC16C711@SOIC18 [DX1033]
PIC16C711@SOIC18(ISP) [DX0001]
PIC16C711@SSOP20 [DX1026]

PIC16C711@SSOP20(ISP) [DX0001]
PIC16C712 [DX0001]
PIC16C712(ISP) [DX0001]
PIC16C712@SOIC18 [DX1033]
PIC16C712@SOIC18(ISP) [DX0001]
PIC16C712@SSOP20 [DX1026]
PIC16C712@SSOP20(ISP) [DX0001]
PIC16C715 [DX0001]
PIC16C715@SOIC18 [DX1033]
PIC16C715@SSOP20 [DX1026]
PIC16C716 [DX0001]
PIC16C716(ISP) [DX0001]
PIC16C716@SOIC18 [DX1033]
PIC16C716@SOIC18(ISP) [DX0001]
PIC16C716@SSOP20 [DX1026]
PIC16C716@SSOP20(ISP) [DX0001]
PIC16C717 [DX0001]
PIC16C717(ISP) [DX0001]
PIC16C717@SOIC18 [DX1033]
PIC16C717@SOIC18(ISP) [DX0001]
PIC16C717@SSOP20 [DX1026]
PIC16C717@SSOP20(ISP) [DX0001]
PIC16C71A [DX0001]
PIC16C71A(ISP) [DX0001]
PIC16C71A@SOIC18 [DX1033]
PIC16C71A@SOIC18(ISP) [DX0001]
PIC16C72 [DX0001]
PIC16C72(ISP) [DX0001]
PIC16C72@SOIC28 [DX1033]
PIC16C72@SOIC28(ISP) [DX0001]
PIC16C72@SSOP28 [DX1026]
PIC16C72@SSOP28(ISP) [DX0001]
PIC16C72A [DX0001]
PIC16C72A(ISP) [DX0001]
PIC16C72A@SOIC28 [DX1033]
PIC16C72A@SOIC28(ISP) [DX0001]
PIC16C72A@SSOP28 [DX1026]
PIC16C72A@SSOP28(ISP) [DX0001]
PIC16C73 [DX0001]
PIC16C73(ISP) [DX0001]
PIC16C73@SOIC28 [DX1033]
PIC16C73@SOIC28(ISP) [DX0001]
PIC16C73A [DX0001]
PIC16C73A(ISP) [DX0001]
PIC16C73A@SOIC28 [DX1033]
PIC16C73A@SOIC28(ISP) [DX0001]
PIC16C73B [DX0001]
PIC16C73B(ISP) [DX0001]
PIC16C73B@SOIC28 [DX1033]
PIC16C73B@SOIC28(ISP) [DX0001]
PIC16C73B@SSOP28 [DX1026]
PIC16C73B@SSOP28(ISP) [DX0001]
PIC16C74 [DX0001]
PIC16C74(ISP) [DX0001]
PIC16C74@PLCC44 [DX2044]
PIC16C74@PLCC44(ISP) [DX0001]
PIC16C74@TQFP44 [DX3003]
PIC16C74@TQFP44(ISP) [DX0001]
PIC16C745 [DX0001]
PIC16C745(ISP) [DX0001]
PIC16C745@SOIC28 [DX1033]
PIC16C745@SOIC28(ISP) [DX0001]
PIC16C74A [DX0001]
PIC16C74A(ISP) [DX0001]
PIC16C74A@PLCC44 [DX2044]
PIC16C74A@PLCC44(ISP) [DX0001]
PIC16C74A@TQFP44 [DX3003]
PIC16C74A@TQFP44(ISP) [DX0001]
PIC16C74B [DX0001]
PIC16C74B(ISP) [DX0001]
PIC16C74B@MQFP44 [DX3002]
PIC16C74B@MQFP44(ISP) [DX0001]
PIC16C74B@PLCC44 [DX2044]
PIC16C74B@PLCC44(ISP) [DX0001]
PIC16C74B@TQFP44 [DX3003]
PIC16C74B@TQFP44(ISP) [DX0001]
PIC16C76 [DX0001]
PIC16C76(ISP) [DX0001]
PIC16C76@SOIC28 [DX1033]
PIC16C76@SOIC28(ISP) [DX0001]
PIC16C765 [DX0001]
PIC16C765(ISP) [DX0001]
PIC16C765@PLCC44 [DX2044]
PIC16C765@PLCC44(ISP) [DX0001]
PIC16C765@TQFP44 [DX3003]
PIC16C765@TQFP44(ISP) [DX0001]
PIC16C77 [DX0001]
PIC16C77(ISP) [DX0001]
PIC16C77@PLCC44 [DX2044]
PIC16C77@PLCC44(ISP) [DX0001]
PIC16C77@TQFP44 [DX3003]
PIC16C77@TQFP44(ISP) [DX0001]
PIC16C770 [DX0001]
PIC16C770(ISP) [DX0001]
PIC16C770@SOIC20 [DX1033]
PIC16C770@SOIC20(ISP) [DX0001]

PIC16C770@SSOP20 [DX1026]
PIC16C771 [DX0001]
PIC16C771@SOIC20 [DX1033]
PIC16C771@SSOP20 [DX1026]
PIC16C773 [DX0001]
PIC16C773@SOIC28 [DX1033]
PIC16C773@SSOP28 [DX1026]
PIC16C774 [DX0001]
PIC16C774@PLCC44 [DX2044]
PIC16C774@TQFP44 [DX3003]
PIC16C781 [DX0001]
PIC16C781@SOIC20 [DX1033]
PIC16C781@SSOP20 [DX1026]
PIC16C782 [DX0001]
PIC16C782@SOIC20 [DX1033]
PIC16C782@SSOP20 [DX1026]
PIC16C84 [DX0001]
PIC16C84@SOIC18 [DX1033]
PIC16C923@PLCC68 [DX2068]
PIC16C923@SDIP64 [DX0064]
PIC16C923@TQFP64 [DX3011]
PIC16C924@PLCC68 [DX2068]
PIC16C924@SDIP64 [DX0064]
PIC16C924@TQFP64 [DX3011]
PIC16C925@PLCC68 [DX2068]
PIC16C925@TQFP64 [DX3011]
PIC16C926@PLCC68 [DX2068]
PIC16C926@TQFP64 [DX3011]
PIC16CE623 [DX0001]
PIC16CE623@SOIC18 [DX1033]
PIC16CE624 [DX0001]
PIC16CE624@SOIC18 [DX1033]
PIC16CE625 [DX0001]
PIC16CE625@SOIC18 [DX1033]
PIC16CE625@SSOP20 [DX1026]
PIC16CR83 [DX0001]
PIC16CR83@SOIC18 [DX1033]
PIC16CR84 [DX0001]
PIC16CR84@SOIC18 [DX1033]
PIC16F1454 [DX0001]
PIC16F1454@QFN16 [DX4010]
PIC16F1454@TSSOP14 [DX1000]
PIC16F1455(ISP) [DX0001]
PIC16F1455@SOIC14 [DX1016]
PIC16F1458 [DX0001]
PIC16F1458@QFN20 [DX4011]
PIC16F1458@SSOP20 [DX1026]
PIC16F1459(ISP) [DX0001]
PIC16C770@SSOP20(ISP) [DX0001]
PIC16C771(ISP) [DX0001]
PIC16C771@SOIC20(ISP) [DX0001]
PIC16C771@SSOP20(ISP) [DX0001]
PIC16C773(ISP) [DX0001]
PIC16C773@SOIC28(ISP) [DX0001]
PIC16C773@SSOP28(ISP) [DX0001]
PIC16C774(ISP) [DX0001]
PIC16C774@PLCC44(ISP) [DX0001]
PIC16C774@TQFP44(ISP) [DX0001]
PIC16C781(ISP) [DX0001]
PIC16C781@SOIC20(ISP) [DX0001]
PIC16C781@SSOP20(ISP) [DX0001]
PIC16C782(ISP) [DX0001]
PIC16C782@SOIC20(ISP) [DX0001]
PIC16C782@SSOP20(ISP) [DX0001]
PIC16C84(ISP) [DX0001]
PIC16C84@SOIC18(ISP) [DX0001]
PIC16C923@PLCC68(ISP) [DX0001]
PIC16C923@SDIP64(ISP) [DX0001]
PIC16C923@TQFP64(ISP) [DX0001]
PIC16C924@PLCC68(ISP) [DX0001]
PIC16C924@SDIP64(ISP) [DX0001]
PIC16C924@TQFP64(ISP) [DX0001]
PIC16C925@PLCC68(ISP) [DX0001]
PIC16C925@TQFP64(ISP) [DX0001]
PIC16C926@PLCC68(ISP) [DX0001]
PIC16C926@TQFP64(ISP) [DX0001]
PIC16CE623(ISP) [DX0001]
PIC16CE623@SOIC18(ISP) [DX0001]
PIC16CE624(ISP) [DX0001]
PIC16CE624@SOIC18(ISP) [DX0001]
PIC16CE625(ISP) [DX0001]
PIC16CE625@SOIC18(ISP) [DX0001]
PIC16CE625@SSOP20(ISP) [DX0001]
PIC16CR83(ISP) [DX0001]
PIC16CR83@SOIC18(ISP) [DX0001]
PIC16CR84(ISP) [DX0001]
PIC16CR84@SOIC18(ISP) [DX0001]
PIC16F1454(ISP) [DX0001]
PIC16F1454@SOIC14 [DX1016]
PIC16F1455 [DX0001]
PIC16F1455@QFN16 [DX4010]
PIC16F1455@TSSOP14 [DX1000]
PIC16F1458(ISP) [DX0001]
PIC16F1458@SOIC20 [DX1033]
PIC16F1459 [DX0001]
PIC16F1459@QFN20 [DX4011]

PIC16F1459@SOIC20 [DX1033]
PIC16F1459@SSOP20 [DX1026]
PIC16F1503 [DX0001]
PIC16F1503(ISP) [DX0001]
PIC16F1503@QFN16 [DX4053]
PIC16F1503@QFN16(ISP) [DX0001]
PIC16F1503@SOIC14 [DX1016]
PIC16F1503@SOIC14(ISP) [DX0001]
PIC16F1503@TSSOP14 [DX1073]
PIC16F1503@TSSOP14(ISP) [DX0001]
PIC16F1507 [DX0001]
PIC16F1507(ISP) [DX0001]
PIC16F1507@QFN20 [DX4011]
PIC16F1507@QFN20(ISP) [DX0001]
PIC16F1507@SOIC20 [DX1033]
PIC16F1507@SOIC20(ISP) [DX0001]
PIC16F1507@SSOP20 [DX1070A]
PIC16F1507@SSOP20(ISP) [DX0001]
PIC16F1508 [DX0001]
PIC16F1508(ISP) [DX0001]
PIC16F1508@QFN20 [DX4011]
PIC16F1508@QFN20(ISP) [DX0001]
PIC16F1508@SOIC20 [DX1033]
PIC16F1508@SOIC20(ISP) [DX0001]
PIC16F1508@SSOP20 [DX1070A]
PIC16F1508@SSOP20(ISP) [DX0001]
PIC16F1509 [DX0001]
PIC16F1509(ISP) [DX0001]
PIC16F1509@QFN20 [DX4011]
PIC16F1509@QFN20(ISP) [DX0001]
PIC16F1509@SOIC20 [DX1033]
PIC16F1509@SOIC20(ISP) [DX0001]
PIC16F1509@SSOP20 [DX1070A]
PIC16F1509@SSOP20(ISP) [DX0001]
PIC16F1512 [DX0001]
PIC16F1512(ISP) [DX0001]
PIC16F1512@SOIC28 [DX1033]
PIC16F1512@SOIC28(ISP) [DX0001]
PIC16F1512@SSOP28 [DX1077]
PIC16F1512@SSOP28(ISP) [DX0001]
PIC16F1512@UQFN28 [DX4036]
PIC16F1512@UQFN28(ISP) [DX0001]
PIC16F1513 [DX0001]
PIC16F1513(ISP) [DX0001]
PIC16F1513@SOIC28 [DX1033]
PIC16F1513@SOIC28(ISP) [DX0001]
PIC16F1513@SSOP28 [DX1077]
PIC16F1513@SSOP28(ISP) [DX0001]
PIC16F1513@UQFN28 [DX4036]
PIC16F1513@UQFN28(ISP) [DX0001]
PIC16F1516 [DX0001]
PIC16F1516(ISP) [DX0001]
PIC16F1516@SOIC28 [DX1033]
PIC16F1516@SOIC28(ISP) [DX0001]
PIC16F1516@SSOP28 [DX1077]
PIC16F1516@SSOP28(ISP) [DX0001]
PIC16F1516@UQFN28 [DX4036]
PIC16F1516@UQFN28(ISP) [DX0001]
PIC16F1517 [DX0001]
PIC16F1517(ISP) [DX0001]
PIC16F1517@TQFP44 [DX3003]
PIC16F1517@TQFP44(ISP) [DX0001]
PIC16F1517@UQFN40 [DX4039]
PIC16F1517@UQFN40(ISP) [DX0001]
PIC16F1518 [DX0001]
PIC16F1518(ISP) [DX0001]
PIC16F1518@SOIC28 [DX1033]
PIC16F1518@SOIC28(ISP) [DX0001]
PIC16F1518@SSOP28 [DX1077]
PIC16F1518@SSOP28(ISP) [DX0001]
PIC16F1518@UQFN28 [DX4036]
PIC16F1518@UQFN28(ISP) [DX0001]
PIC16F1519 [DX0001]
PIC16F1519(ISP) [DX0001]
PIC16F1519@TQFP44 [DX3003]
PIC16F1519@TQFP44(ISP) [DX0001]
PIC16F1519@UQFN40 [DX4039]
PIC16F1519@UQFN40(ISP) [DX0001]
PIC16F1526@QFN64 [DX3011]
PIC16F1526@QFN64(ISP) [DX0001]
PIC16F1526@TQFP64 [DX3011]
PIC16F1526@TQFP64(ISP) [DX0001]
PIC16F1527@QFN64 [DX3011]
PIC16F1527@QFN64(ISP) [DX0001]
PIC16F1527@TQFP64 [DX3011]
PIC16F1527@TQFP64(ISP) [DX0001]
PIC16F1574 [DX0001]
PIC16F1574@ISP [DX0001]
PIC16F1574@QFN16 [DX4053]
PIC16F1574@SOIC14 [DX1016]
PIC16F1574@TSSOP14 [DX1000]
PIC16F1575 [DX0001]
PIC16F1575@ISP [DX0001]
PIC16F1575-Q16 [DX4053]
PIC16F1575-S14 [DX1016]
PIC16F1575-T14 [DX1000]

PIC16F1578 [DX0001]
PIC16F1578@ISP [DX0001]
PIC16F1578-Q20 [DX4011]
PIC16F1578-S20 [DX1033]
PIC16F1578-SS20 [DX1070]
PIC16F1579 [DX0001]
PIC16F1579@ISP [DX0001]
PIC16F1579-Q20 [DX4011]
PIC16F1579-S20 [DX1033]
PIC16F1579-SS20 [DX1070]
PIC16F1703 [DX0001]
PIC16F1703@ISP [DX0001]
PIC16F1703@QFN16 [DX4053]
PIC16F1703@SOIC14 [DX1016]
PIC16F1703@TSSOP14 [DX1000]
PIC16F1704 [DX0001]
PIC16F1704@ISP [DX0001]
PIC16F1704@QFN16 [DX4053]
PIC16F1704@SOIC14 [DX1016]
PIC16F1704@TSSOP14 [DX1000]
PIC16F1705 [DX0001]
PIC16F1705@ISP [DX0001]
PIC16F1705@QFN16 [DX4053]
PIC16F1705@SOIC14 [DX1016]
PIC16F1705@TSSOP14 [DX1000]
PIC16F1707 [DX0001]
PIC16F1707@ISP [DX0001]
PIC16F1707@QFN20 [DX4011]
PIC16F1707@SOIC20 [DX1033]
PIC16F1707@SSOP20 [DX1070]
PIC16F1708 [DX0001]
PIC16F1708@ISP [DX0001]
PIC16F1708@QFN20 [DX4011]
PIC16F1708@SOIC20 [DX1033]
PIC16F1708@SSOP20 [DX1070]
PIC16F1709 [DX0001]
PIC16F1709@ISP [DX0001]
PIC16F1709@QFN20 [DX4011]
PIC16F1709@SOIC20 [DX1033]
PIC16F1709@SSOP20 [DX1070]
PIC16F1782 [DX0001]
PIC16F1782(ISP) [DX0001]
PIC16F1782@SOIC28 [DX1033]
PIC16F1782@SOIC28(ISP) [DX0001]
PIC16F1782@SSOP28 [DX1026]
PIC16F1782@SSOP28(ISP) [DX0001]
PIC16F1782@UQFN28 [DX4014]
PIC16F1782@UQFN28(ISP) [DX0001]
PIC16F1783 [DX0001]
PIC16F1783(ISP) [DX0001]
PIC16F1783@SOIC28 [DX1033]
PIC16F1783@SOIC28(ISP) [DX0001]
PIC16F1783@SSOP28 [DX1026]
PIC16F1783@SSOP28(ISP) [DX0001]
PIC16F1783@UQFN28 [DX4014]
PIC16F1783@UQFN28(ISP) [DX0001]
PIC16F1784 [DX0001]
PIC16F1784(ISP) [DX0001]
PIC16F1784@QFN44 [DX4019]
PIC16F1784@TQFP44 [DX3003]
PIC16F1784@UQFN40
PIC16F1786 [DX0001]
PIC16F1786(ISP) [DX0001]
PIC16F1786@QFN28 [DX4014]
PIC16F1786@SOIC28 [DX1033]
PIC16F1786@SSOP28 [DX1026]
PIC16F1787 [DX0001]
PIC16F1787(ISP) [DX0001]
PIC16F1787@QFN44 [DX4019]
PIC16F1787@TQFP44 [DX3003]
PIC16F1787@UQFN40
PIC16F1788 [DX0001]
PIC16F1788(ISP) [DX0001]
PIC16F1788@QFN28 [DX4014]
PIC16F1788@SOIC28 [DX1033]
PIC16F1788@SSOP28 [DX1026]
PIC16F1789 [DX0001]
PIC16F1789(ISP) [DX0001]
PIC16F1789@QFN44 [DX4019]
PIC16F1789@TQFP44 [DX3003]
PIC16F1789@UQFN40
PIC16F1823 [DX0001]
PIC16F1823(8-word) [DX0001]
PIC16F1823(ISP)(HV) [DX0001]
PIC16F1823(LV) [DX0001]
PIC16F1823(LVISP) [DX0001]
PIC16F1823@QFN16(3*3) [DX4008]
PIC16F1823@QFN16(3*3)(8-word) [DX4008]
PIC16F1823@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16F1823@QFN16(3*3)(LV) [DX4008]
PIC16F1823@QFN16(4*4) [DX4010]

PIC16F1823@QFN16(4*4)(8-word) [DX4010]
PIC16F1823@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16F1823@QFN16(4*4)(LV) [DX4010]
PIC16F1823@SOIC14 [DX1016]
PIC16F1823@SOIC14(8-word) [DX1016]
PIC16F1823@SOIC14(ISP)(HV) [DX0001]
PIC16F1823@SOIC14(LV) [DX1016] PIC16F1823@TSSOP14 [DX1073]
PIC16F1823@TSSOP14(8-word) [DX1073]
PIC16F1823@TSSOP14(ISP)(HV) [DX0001]
PIC16F1823@TSSOP14(LV) [DX1000] PIC16F1824 [DX0001]
PIC16F1824(8-word) [DX0001] PIC16F1824(ISP)(HV) [DX0001]
PIC16F1824(LV) [DX0001] PIC16F1824(LVISP) [DX0001]
PIC16F1824@QFN16(3*3) [DX4008]
PIC16F1824@QFN16(3*3)(8-word) [DX4008]
PIC16F1824@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16F1824@QFN16(3*3)(LV) [DX4008]
PIC16F1824@QFN16(4*4) [DX4010]
PIC16F1824@QFN16(4*4)(8-word) [DX4010]
PIC16F1824@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16F1824@QFN16(4*4)(LV) [DX4010]
PIC16F1824@SOIC14 [DX1016]
PIC16F1824@SOIC14(8-word) [DX1016]
PIC16F1824@SOIC14(ISP)(HV) [DX0001]
PIC16F1824@SOIC14(LV) [DX1016] PIC16F1824@TSSOP14 [DX1073]
PIC16F1824@TSSOP14(8-word) [DX1073]
PIC16F1824@TSSOP14(ISP)(HV) [DX0001]
PIC16F1824@TSSOP14(LV) [DX1000] PIC16F1825 [DX0001]
PIC16F1825(8-word) [DX0001] PIC16F1825(ISP)(HV) [DX0001]
PIC16F1825(LV) [DX0001] PIC16F1825(LVISP) [DX0001]
PIC16F1825@QFN16(3*3) [DX4008]
PIC16F1825@QFN16(3*3)(8-word) [DX4008]
PIC16F1825@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16F1825@QFN16(3*3)(LV) [DX4008]
PIC16F1825@QFN16(4*4) [DX4010]
PIC16F1825@QFN16(4*4)(8-word) [DX4010]
PIC16F1825@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16F1825@QFN16(4*4)(LV) [DX4010]
PIC16F1825@SOIC14 [DX1016]
PIC16F1825@SOIC14(8-word) [DX1016]
PIC16F1825@SOIC14(ISP)(HV) [DX0001]
PIC16F1825@SOIC14(LV) [DX1016] PIC16F1825@TSSOP14 [DX1073]
PIC16F1825@TSSOP14(8-word) [DX1073]
PIC16F1825@TSSOP14(ISP)(HV) [DX0001]
PIC16F1825@TSSOP14(LV) [DX1000] PIC16F1826 [DX0001]
PIC16F1826(8-word) [DX0001] PIC16F1826(ISP)(HV) [DX0001]
PIC16F1826(LV) [DX0001] PIC16F1826(LVISP) [DX0001]
PIC16F1826@QFN28 [DX4014]
PIC16F1826@QFN28(8-word) [DX4014]

PIC16F1826@QFN28(ISP)(HV) [DX0001]
PIC16F1826@QFN28(LV) [DX4014]
PIC16F1826@SOIC18 [DX1033]
PIC16F1826@SOIC18(8-word) [DX1033]
PIC16F1826@SOIC18(ISP)(HV) [DX0001]
PIC16F1826@SOIC18(LV) [DX1033]
PIC16F1826@SSOP20 [DX1070]
PIC16F1826@SSOP20(8-word) [DX1070]
PIC16F1826@SSOP20(ISP)(HV) [DX0001]
PIC16F1826@SSOP20(LV) [DX1026]
PIC16F1826@UQFN28 [DX4036]
PIC16F1826@UQFN28(8-word) [DX4036]
PIC16F1827 [DX0001]
PIC16F1827(8-word) [DX0001]
PIC16F1827(ISP)(HV) [DX0001]
PIC16F1827(LV) [DX0001]
PIC16F1827(LVISP) [DX0001]
PIC16F1827@QFN28 [DX4014]
PIC16F1827@QFN28(8-word) [DX4014]
PIC16F1827@QFN28(ISP)(HV) [DX0001]
PIC16F1827@QFN28(LV) [DX4014]
PIC16F1827@SOIC18 [DX1033]
PIC16F1827@SOIC18(8-word) [DX1033]
PIC16F1827@SOIC18(ISP)(HV) [DX0001]
PIC16F1827@SOIC18(LV) [DX1033]
PIC16F1827@SSOP20 [DX1070]
PIC16F1827@SSOP20(8-word) [DX1070]
PIC16F1827@SSOP20(ISP)(HV) [DX0001]
PIC16F1827@SSOP20(LV) [DX1026]
PIC16F1827@UQFN28 [DX4036]
PIC16F1827@UQFN28(8-word) [DX4036]
PIC16F1828 [DX0001]
PIC16F1828(8-word) [DX0001]
PIC16F1828(ISP)(HV) [DX0001]
PIC16F1828(LV) [DX0001]
PIC16F1828(LVISP) [DX0001]
PIC16F1828@QFN20 [DX4011]
PIC16F1828@QFN20(8-word) [DX4011]
PIC16F1828@QFN20(ISP)(HV) [DX0001]
PIC16F1828@QFN20(LV) [DX4011]
PIC16F1828@SOIC20 [DX1033]
PIC16F1828@SOIC20(8-word) [DX1033]
PIC16F1828@SOIC20(ISP)(HV) [DX0001]
PIC16F1828@SOIC20(LV) [DX1033]
PIC16F1828@TSSOP20 [DX1070]
PIC16F1828@TSSOP20(8-word) [DX1070]
PIC16F1828@TSSOP20(ISP)(HV) [DX0001]
PIC16F1828@TSSOP20(LV) [DX1026]
PIC16F1829 [DX0001]
PIC16F1829(8-word) [DX0001]
PIC16F1829(ISP)(HV) [DX0001]
PIC16F1829(LV) [DX0001]
PIC16F1829(LVISP) [DX0001]
PIC16F1829@QFN20 [DX4011]
PIC16F1829@QFN20(8-word) [DX4011]
PIC16F1829@QFN20(ISP)(HV) [DX0001]
PIC16F1829@QFN20(LV) [DX4011]
PIC16F1829@SOIC20 [DX1033]
PIC16F1829@SOIC20(8-word) [DX1033]
PIC16F1829@SOIC20(ISP)(HV) [DX0001]
PIC16F1829@SOIC20(LV) [DX1033]
PIC16F1829@TSSOP20 [DX1070]
PIC16F1829@TSSOP20(8-word) [DX1070]
PIC16F1829@TSSOP20(ISP)(HV) [DX0001]
PIC16F1829@TSSOP20(LV) [DX1026]
PIC16F1847 [DX0001]
PIC16F1847(ISP)(HV) [DX0001]
PIC16F1847@QFN28 [DX4014]
PIC16F1847@QFN28(ISP)(HV) [DX0001]

PIC16F1847@SOIC18 [DX1033]
PIC16F1847@SOIC18(ISP)(HV) [DX0001]
PIC16F1847@SSOP20 [DX1026]
PIC16F1847@SSOP20(ISP)(HV) [DX0001]
PIC16F1847E [DX0001]
PIC16F1847E@QFN28 [DX4014]
PIC16F1847E@SOIC18 [DX1033]
PIC16F1847E@SSOP20 [DX1026]
PIC16F1933 [DX0001]
PIC16F1933(ISP)(HV) [DX0001]
PIC16F1933@QFN28 [DX4014]
PIC16F1933@QFN28(ISP)(HV) [DX0001]
PIC16F1933@QFN28[8-word pro] [DX4014]
PIC16F1933@SOIC28 [DX1033]
PIC16F1933@SOIC28(ISP)(HV) [DX0001]
PIC16F1933@SOIC28[8-word pro] [DX1033]
PIC16F1933@SSOP28 [DX1077]
PIC16F1933@SSOP28(ISP)(HV) [DX0001]
PIC16F1933@SSOP28[8-word pro] [DX1077]
PIC16F1933@UQFN28 [DX4036]
PIC16F1933[8-word pro] [DX0001]
PIC16F1934 [DX0001]
PIC16F1934(ISP)(HV) [DX0001]
PIC16F1934@QFN44 [DX4019]
PIC16F1934@QFN44(ISP)(HV) [DX0001]
PIC16F1934@QFN44[8-word pro] [DX4019]
PIC16F1934@TQFP44 [DX3003]
PIC16F1934@TQFP44(ISP)(HV) [DX0001]
PIC16F1934@TQFP44[8-word pro] [DX3003]
PIC16F1934[8-word pro] [DX0001]
PIC16F1936 [DX0001]
PIC16F1936(ISP)(HV) [DX0001]
PIC16F1936@QFN28 [DX4014]
PIC16F1936@QFN28(ISP)(HV) [DX0001]
PIC16F1936@QFN28[8-word pro] [DX4014]
PIC16F1936@SOIC28 [DX1033]
PIC16F1936@SOIC28(ISP)(HV) [DX0001]
PIC16F1936@SOIC28[8-word pro] [DX1033]
PIC16F1936@SSOP28 [DX1077]
PIC16F1936@SSOP28(ISP)(HV) [DX0001]
PIC16F1936@SSOP28[8-word pro] [DX1077]
PIC16F1936@UQFN28 [DX4036]
PIC16F1936[8-word pro] [DX0001]
PIC16F1937 [DX0001]
PIC16F1937(ISP)(HV) [DX0001]
PIC16F1937@QFN44 [DX4019]
PIC16F1937@QFN44(ISP)(HV) [DX0001]
PIC16F1937@QFN44[8-word pro] [DX4019]
PIC16F1937@TQFP44 [DX3003]
PIC16F1937@TQFP44(ISP)(HV) [DX0001]
PIC16F1937@TQFP44[8-word pro] [DX3003]
PIC16F1937[8-word pro] [DX0001]
PIC16F1938 [DX0001]
PIC16F1938(ISP)(HV) [DX0001]
PIC16F1938@QFN28 [DX4014]
PIC16F1938@QFN28(ISP)(HV) [DX0001]
PIC16F1938@QFN28[8-word pro] [DX4014]
PIC16F1938@SOIC28 [DX1033]
PIC16F1938@SOIC28(ISP)(HV) [DX0001]

PIC16F1938@SOIC28[8-word pro] [DX1033]
PIC16F1938@SSOP28 [DX1077]
PIC16F1938@SSOP28(ISP)(HV) [DX0001]
PIC16F1938@SSOP28[8-word pro] [DX1077]
PIC16F1938@UQFN28 [DX4036]
PIC16F1938[8-word pro] [DX0001]
PIC16F1939 [DX0001]
PIC16F1939(ISP)(HV) [DX0001]
PIC16F1939@QFN44 [DX4019]
PIC16F1939@QFN44(ISP)(HV) [DX0001]
PIC16F1939@QFN44[8-word pro] [DX4019]
PIC16F1939@TQFP44 [DX3003]
PIC16F1939@TQFP44(ISP)(HV) [DX0001]
PIC16F1939@TQFP44[8-word pro] [DX3003]
PIC16F1939[8-word pro] [DX0001]
PIC16F1946@QFN64 [DX4023]
PIC16F1946@QFN64(ISP)(HV) [DX0001]
PIC16F1946@QFN64[8-word pro] [DX4023]
PIC16F1946@TQFP64 [DX3011]
PIC16F1946@TQFP64(ISP)(HV) [DX0001]
PIC16F1946@TQFP64[8-word pro] [DX3011]
PIC16F1947@QFN64 [DX4023]
PIC16F1947@QFN64(ISP)(HV) [DX0001]
PIC16F1947@QFN64[8-word pro] [DX4023]
PIC16F1947@TQFP64 [DX3011]
PIC16F1947@TQFP64(ISP)(HV) [DX0001]
PIC16F1947@TQFP64[8-word pro] [DX3011]
PIC16F505 [DX0001]
PIC16F505(ISP) [DX0001]
PIC16F505@SOIC14 [DX1065]
PIC16F505@SOIC14(ISP) [DX0001]
PIC16F505@TSSOP14 [DX1000]
PIC16F505@TSSOP14(ISP) [DX0001]
PIC16F506 [DX0001]
PIC16F506(ISP) [DX0001]
PIC16F506@SOIC14 [DX1030]
PIC16F506@SOIC14(ISP) [DX0001]
PIC16F506@TSSOP14 [DX1001]
PIC16F506@TSSOP14(ISP) [DX0001]
PIC16F526 [DX0001]
PIC16F526(ISP) [DX0001]
PIC16F526@SOIC14 [DX1016]
PIC16F526@SOIC14(ISP) [DX0001]
PIC16F526@TSSOP14 [DX1000]
PIC16F526@TSSOP14(ISP) [DX0001]
PIC16F527 [DX0001]
PIC16F527(ISP) [DX0001]
PIC16F527@QFN20 [DX4011]
PIC16F527@SOIC20 [DX1033]
PIC16F527@SSOP20 [DX1026]
PIC16F54 [DX0001]
PIC16F54(ISP) [DX0001]
PIC16F54@SOIC18 [DX1033]
PIC16F54@SOIC18(ISP) [DX0001]
PIC16F54@SSOP20 [DX1026]
PIC16F54@SSOP20(ISP) [DX0001]
PIC16F57 [DX0001]
PIC16F57(ISP) [DX0001]
PIC16F57@SOIC28 [DX1033]
PIC16F57@SOIC28(ISP) [DX0001]
PIC16F57@SSOP28 [DX1026]
PIC16F57@SSOP28(ISP) [DX0001]
PIC16F59 [DX0001]
PIC16F59(ISP) [DX0001]
PIC16F59@PLCC44 [DX2044]
PIC16F59@PLCC44(ISP) [DX0001]
PIC16F59@TQFP44 [DX3003]
PIC16F59@TQFP44(ISP) [DX0001]
PIC16F610 [DX0001]
PIC16F610(ISP) [DX0001]
PIC16F610@QFN16 [DX4010]
PIC16F610@QFN16(ISP) [DX0001]
PIC16F610@SOIC14 [DX1016]
PIC16F610@SOIC14(ISP) [DX0001]
PIC16F610@TSSOP14 [DX1000]

PIC16F610@TSSOP14(ISP) [DX0001]
PIC16F616 [DX0001]
PIC16F616(ISP) [DX0001]
PIC16F616@QFN16 [DX4010]
PIC16F616@QFN16(ISP) [DX0001]
PIC16F616@SOIC14 [DX1016]
PIC16F616@SOIC14(ISP) [DX0001]
PIC16F616@TSSOP14 [DX1000]
PIC16F616@TSSOP14(ISP) [DX0001]
PIC16F627 [DX0001]
PIC16F627(ISP) [DX0001]
PIC16F627@SOIC18 [DX1033]
PIC16F627@SOIC18(ISP) [DX0001]
PIC16F627@SSOP20 [DX1026]
PIC16F627@SSOP20(ISP) [DX0001]
PIC16F627A [DX0001]
PIC16F627A(ISP) [DX0001]
PIC16F627A@SOIC18 [DX1033]
PIC16F627A@SOIC18(ISP) [DX0001]
PIC16F627A@SSOP20 [DX1026]
PIC16F627A@SSOP20(ISP) [DX0001]
PIC16F628 [DX0001]
PIC16F628(ISP) [DX0001]
PIC16F628@SOIC18 [DX1033]
PIC16F628@SOIC18(ISP) [DX0001]
PIC16F628@SSOP20 [DX1026]
PIC16F628@SSOP20(ISP) [DX0001]
PIC16F628A [DX0001]
PIC16F628A(ISP) [DX0001]
PIC16F628A@SOIC18 [DX1033]
PIC16F628A@SOIC18(ISP) [DX0001]
PIC16F628A@SSOP20 [DX1026]
PIC16F628A@SSOP20(ISP) [DX0001]
PIC16F630 [DX0001]
PIC16F630(ISP) [DX0001]
PIC16F630@SOIC14 [DX1065]
PIC16F630@SOIC14(ISP) [DX0001]
PIC16F630@TSSOP14 [DX1000]
PIC16F630@TSSOP14(ISP) [DX0001]
PIC16F631 [DX0001]
PIC16F631(ISP) [DX0001]
PIC16F631@QFN20 [DX4011]
PIC16F631@QFN20(ISP) [DX0001]
PIC16F631@SOIC20 [DX1033]
PIC16F631@SOIC20(ISP) [DX0001]
PIC16F631@SSOP20 [DX1070]
PIC16F631@SSOP20(ISP) [DX0001]
PIC16F636 [DX0001]
PIC16F636(4-WORD PRO) [DX0001]
PIC16F636(ISP) [DX0001]
PIC16F636@QFN16 [DX4010]
PIC16F636@QFN16(4-WORD PRO) [DX4010]
PIC16F636@QFN16(ISP) [DX0001]
PIC16F636@SOIC14 [DX1065]
PIC16F636@SOIC14(4-WORD PRO) [DX1065]
PIC16F636@SOIC14(ISP) [DX0001]
PIC16F636@TSSOP14 [DX1000]
PIC16F636@TSSOP14(4-WORD PRO) [DX1000]
PIC16F636@TSSOP14(ISP) [DX0001]
PIC16F639 [DX0001]
PIC16F639(ISP) [DX0001]
PIC16F639@QFN20 [DX4011]
PIC16F639@QFN20(ISP) [DX0001]
PIC16F639@SOIC20 [DX1033]
PIC16F639@SOIC20(ISP) [DX0001]
PIC16F639@SSOP20 [DX1070]
PIC16F639@SSOP20(ISP) [DX0001]
PIC16F648A [DX0001]
PIC16F648A(ISP) [DX0001]
PIC16F648A@SOIC18 [DX1033]
PIC16F648A@SOIC18(ISP) [DX0001]
PIC16F648A@SSOP20 [DX1026]
PIC16F648A@SSOP20(ISP) [DX0001]
PIC16F676 [DX0001]
PIC16F676(ISP) [DX0001]
PIC16F676@SOIC14 [DX1065]
PIC16F676@SOIC14(ISP) [DX0001]
PIC16F676@TSSOP14 [DX1000]
PIC16F676@TSSOP14(ISP) [DX0001]
PIC16F677 [DX0001]
PIC16F677(ISP) [DX0001]
PIC16F677@QFN20 [DX4011]
PIC16F677@QFN20(ISP) [DX0001]
PIC16F677@SOIC20 [DX1033]
PIC16F677@SOIC20(ISP) [DX0001]
PIC16F677@SSOP20 [DX1070]
PIC16F677@SSOP20(ISP) [DX0001]
PIC16F684 [DX0001]
PIC16F684(4-WORD PRO) [DX0001]
PIC16F684(ISP) [DX0001]
PIC16F684@QFN16 [DX4010]

PIC16F684@QFN16(4-WORD PRO) [DX4010]
PIC16F684@QFN16(ISP) [DX0001]　　PIC16F684@SOIC14 [DX1065]
PIC16F684@SOIC14(4-WORD PRO) [DX1065]
PIC16F684@SOIC14(ISP) [DX0001]　　PIC16F684@TSSOP14 [DX1000]
PIC16F684@TSSOP14(4-WORD PRO) [DX1000]
PIC16F684@TSSOP14(ISP) [DX0001]　　PIC16F685 [DX0001]
PIC16F685(ISP) [DX0001]　　PIC16F685@QFN20 [DX4011]
PIC16F685@QFN20(ISP) [DX0001]　　PIC16F685@SOIC20 [DX1033]
PIC16F685@SOIC20(ISP) [DX0001]　　PIC16F685@SSOP20 [DX1070]
PIC16F685@SSOP20(ISP) [DX0001]　　PIC16F687 [DX0001]
PIC16F687(ISP) [DX0001]　　PIC16F687@QFN20 [DX4011]
PIC16F687@QFN20(ISP) [DX0001]　　PIC16F687@SOIC20 [DX1033]
PIC16F687@SOIC20(ISP) [DX0001]　　PIC16F687@SSOP20 [DX1070]
PIC16F687@SSOP20(ISP) [DX0001]　　PIC16F688 [DX0001]
PIC16F688(4-WORD PRO) [DX0001]　　PIC16F688(ISP) [DX0001]
PIC16F688@QFN16 [DX4010]
PIC16F688@QFN16(4-WORD PRO) [DX4010]
PIC16F688@QFN16(ISP) [DX0001]　　PIC16F688@SOIC14 [DX1065]
PIC16F688@SOIC14(4-WORD PRO) [DX1065]
PIC16F688@SOIC14(ISP) [DX0001]　　PIC16F688@TSSOP14 [DX1000]
PIC16F688@TSSOP14(4-WORD PRO) [DX1000]
PIC16F688@TSSOP14(ISP) [DX0001]　　PIC16F689 [DX0001]
PIC16F689(ISP) [DX0001]　　PIC16F689@QFN20 [DX4011]
PIC16F689@QFN20(ISP) [DX0001]　　PIC16F689@SOIC20 [DX1033]
PIC16F689@SOIC20(ISP) [DX0001]　　PIC16F689@SSOP20 [DX1070]
PIC16F689@SSOP20(ISP) [DX0001]　　PIC16F690 [DX0001]
PIC16F690(ISP) [DX0001]　　PIC16F690@QFN20 [DX4011]
PIC16F690@QFN20(ISP) [DX0001]　　PIC16F690@SOIC20 [DX1033]
PIC16F690@SOIC20(ISP) [DX0001]　　PIC16F690@SSOP20 [DX1070]
PIC16F690@SSOP20(ISP) [DX0001]
PIC16F690@SSOP20(REVERSE) [DX1070]
PIC16F707 [DX0001]　　PIC16F707(ISP) [DX0001]
PIC16F707@QFN44 [DX4019]　　PIC16F707@QFN44(ISP) [DX0001]
PIC16F707@TQFP44 [DX3003]　　PIC16F707@TQFP44(ISP) [DX0001]
PIC16F716 [DX0001]　　PIC16F716(4-WORD PRO) [DX0001]
PIC16F716(ISP) [DX0001]　　PIC16F716@SOIC18 [DX1033]
PIC16F716@SOIC18(4-WORD PRO) [DX1033]
PIC16F716@SOIC18(ISP) [DX0001]　　PIC16F716@SSOP20 [DX1026]
PIC16F716@SSOP20(4-WORD PRO) [DX1026]
PIC16F716@SSOP20(ISP) [DX0001]　　PIC16F72 [DX0001]
PIC16F72(ISP) [DX0001]　　PIC16F72@QFN28 [DX4014]
PIC16F72@QFN28(ISP) [DX0001]　　PIC16F72@SOIC28 [DX1033]
PIC16F72@SOIC28(ISP) [DX0001]　　PIC16F72@SSOP28 [DX1026]
PIC16F72@SSOP28(ISP) [DX0001]　　PIC16F720 [DX0001]
PIC16F720@QFN20 [DX4011]　　PIC16F720@SOIC20 [DX1033]
PIC16F720@SSOP20 [DX1026]　　PIC16F721 [DX0001]
PIC16F721@QFN20 [DX4011]　　PIC16F721@SOIC20 [DX1033]
PIC16F721@SSOP20 [DX1026]　　PIC16F722 [DX0001]

PIC16F722(ISP) [DX0001]
PIC16F722@QFN28(ISP) [DX0001]
PIC16F722@SOIC28(ISP) [DX0001]
PIC16F722@SSOP28(ISP) [DX0001]
PIC16F722A(ISP) [DX0001]
PIC16F722A@QFN28(ISP) [DX0001]
PIC16F722A@SOIC28(ISP) [DX0001]
PIC16F722A@SSOP28(ISP) [DX0001]
PIC16F723(ISP) [DX0001]
PIC16F723@QFN28(ISP) [DX0001]
PIC16F723@SOIC28(ISP) [DX0001]
PIC16F723@SSOP28(ISP) [DX0001]
PIC16F723A(ISP) [DX0001]
PIC16F723A@QFN28(ISP) [DX0001]
PIC16F723A@SOIC28(ISP) [DX0001]
PIC16F723A@SSOP28(ISP) [DX0001]
PIC16F724(ISP) [DX0001]
PIC16F724@QFN44(ISP) [DX0001]
PIC16F724@TQFP44(ISP) [DX0001]
PIC16F726(ISP) [DX0001]
PIC16F726@QFN28(ISP) [DX0001]
PIC16F726@SOIC28(ISP) [DX0001]
PIC16F726@SSOP28(ISP) [DX0001]
PIC16F727(ISP) [DX0001]
PIC16F727@QFN44(ISP) [DX0001]
PIC16F727@TQFP44(ISP) [DX0001]
PIC16F73(ISP) [DX0001]
PIC16F73@SOIC28 [DX1033]
PIC16F73@SSOP28 [DX1026]
PIC16F737 [DX0001]
PIC16F737@SOIC28 [DX1033]
PIC16F737@SSOP28 [DX1077]
PIC16F74 [DX0001]
PIC16F74@PLCC44 [DX2044]
PIC16F74@TQFP44 [DX3003]
PIC16F747 [DX0001]
PIC16F747@TQFP44 [DX3003]
PIC16F753 [DX0001]
PIC16F753@SOIC14 [DX1016]
PIC16F76 [DX0001]
PIC16F76@QFN28 [DX4014]
PIC16F76@SOIC28(ISP) [DX0001]
PIC16F76@SSOP28(ISP) [DX0001]
PIC16F767(ISP) [DX0001]
PIC16F767@SOIC28(ISP) [DX0001]
PIC16F767@SSOP28(ISP) [DX0001]
PIC16F77(ISP) [DX0001]
PIC16F77@PLCC44(ISP) [DX0001]
PIC16F722@QFN28 [DX4014]
PIC16F722@SOIC28 [DX1033]
PIC16F722@SSOP28 [DX1077]
PIC16F722A [DX0001]
PIC16F722A@QFN28 [DX4014]
PIC16F722A@SOIC28 [DX1033]
PIC16F722A@SSOP28 [DX1077]
PIC16F723 [DX0001]
PIC16F723@QFN28 [DX4014]
PIC16F723@SOIC28 [DX1033]
PIC16F723@SSOP28 [DX1077]
PIC16F723A [DX0001]
PIC16F723A@QFN28 [DX4014]
PIC16F723A@SOIC28 [DX1033]
PIC16F723A@SSOP28 [DX1077]
PIC16F724 [DX0001]
PIC16F724@QFN44 [DX4019]
PIC16F724@TQFP44 [DX3003]
PIC16F726 [DX0001]
PIC16F726@QFN28 [DX4014]
PIC16F726@SOIC28 [DX1033]
PIC16F726@SSOP28 [DX1077]
PIC16F727 [DX0001]
PIC16F727@QFN44 [DX4019]
PIC16F727@TQFP44 [DX3003]
PIC16F73 [DX0001]
PIC16F73@QFN28 [DX4014]
PIC16F73@SOIC28(ISP) [DX0001]
PIC16F73@SSOP28(ISP) [DX0001]
PIC16F737(ISP) [DX0001]
PIC16F737@SOIC28(ISP) [DX0001]
PIC16F737@SSOP28(ISP) [DX0001]
PIC16F74(ISP) [DX0001]
PIC16F74@PLCC44(ISP) [DX0001]
PIC16F74@TQFP44(ISP) [DX0001]
PIC16F747(ISP) [DX0001]
PIC16F747@TQFP44(ISP) [DX0001]
PIC16F753(ISP) [DX0001]
PIC16F753@TSSOP14 [DX1073]
PIC16F76(ISP) [DX0001]
PIC16F76@SOIC28 [DX1033]
PIC16F76@SSOP28 [DX1026]
PIC16F767 [DX0001]
PIC16F767@SOIC28 [DX1033]
PIC16F767@SSOP28 [DX1077]
PIC16F77 [DX0001]
PIC16F77@PLCC44 [DX2044]
PIC16F77@TQFP44 [DX3003]

PIC16F77@TQFP44(ISP) [DX0001]
PIC16F777(ISP) [DX0001]
PIC16F777@TQFP44(ISP) [DX0001]
PIC16F785(ISP) [DX0001]
PIC16F785@QFN20(ISP) [DX0001]
PIC16F785@SOIC20(ISP) [DX0001]
PIC16F785@SSOP20(ISP) [DX0001]
PIC16F818(ISP) [DX0001]
PIC16F818@QFN28(ISP) [DX0001]
PIC16F818@SOIC18(ISP) [DX0001]
PIC16F818@SSOP20(ISP) [DX0001]
PIC16F819(ISP) [DX0001]
PIC16F819@QFN28(ISP) [DX0001]
PIC16F819@SOIC18(ISP) [DX0001]
PIC16F819@SSOP20(ISP) [DX0001]
PIC16F83(ISP) [DX0001]
PIC16F83@SOIC18(ISP) [DX0001]
PIC16F84(ISP) [DX0001]
PIC16F84@SOIC18(ISP) [DX0001]
PIC16F84A(ISP) [DX0001]
PIC16F84A@SOIC18(ISP) [DX0001]
PIC16F84A@SSOP20(ISP) [DX0001]
PIC16F87(ISP) [DX0001]
PIC16F87@QFN28(ISP) [DX0001]
PIC16F87@SOIC18(ISP) [DX0001]
PIC16F87@SSOP20(ISP) [DX0001]
PIC16F870(ISP) [DX0001]
PIC16F870@SOIC28(ISP)
PIC16F870@SSOP28(ISP)
PIC16F871(ISP)
PIC16F871@MQFP44(ISP)
PIC16F871@PLCC44(ISP)
PIC16F871@TQFP44(ISP)
PIC16F872(ISP)
PIC16F872@SOIC28(ISP)
PIC16F872@SSOP28(ISP)
PIC16F873(ISP)
PIC16F873@SOIC28(ISP)
PIC16F873A(ISP)(High-V) [DX0001]
PIC16F873A(ISP3.3v)(HV) [DX0001]
PIC16F873A@QFN28 [DX4014]
PIC16F873A@QFN28(ISP)(High-V) [DX0001]
PIC16F873A@QFN28(ISP)(Low-V) [DX0001]
PIC16F873A@QFN28(ISP3.3v)(HV) [DX0001]
PIC16F873A@QFN28(ISP3.3v)(LV) [DX0001]
PIC16F873A@SOIC28 [DX1033]
PIC16F873A@SOIC28(ISP)(High-V) [DX0001]
PIC16F873A@SOIC28(ISP)(Low-V) [DX0001]
PIC16F777 [DX0001]
PIC16F777@TQFP44 [DX3003]
PIC16F785 [DX0001]
PIC16F785@QFN20 [DX4011]
PIC16F785@SOIC20 [DX1033]
PIC16F785@SSOP20 [DX1026]
PIC16F818 [DX0001]
PIC16F818@QFN28 [DX4014]
PIC16F818@SOIC18 [DX1033]
PIC16F818@SSOP20 [DX1026]
PIC16F819 [DX0001]
PIC16F819@QFN28 [DX4014]
PIC16F819@SOIC18 [DX1033]
PIC16F819@SSOP20 [DX1026]
PIC16F83 [DX0001]
PIC16F83@SOIC18 [DX1033]
PIC16F84 [DX0001]
PIC16F84@SOIC18 [DX1033]
PIC16F84A [DX0001]
PIC16F84A@SOIC18 [DX1033]
PIC16F84A@SSOP20 [DX1026]
PIC16F87 [DX0001]
PIC16F87@QFN28 [DX4014]
PIC16F87@SOIC18 [DX1033]
PIC16F87@SSOP20 [DX1026]
PIC16F870 [DX0001]
PIC16F870@SOIC28 [DX1033]
PIC16F870@SSOP28 [DX1026]
PIC16F871 [DX0001]
PIC16F871@MQFP44 [DX3088]
PIC16F871@PLCC44 [DX2044]
PIC16F871@TQFP44 [DX3003]
PIC16F872 [DX0001]
PIC16F872@SOIC28 [DX1033]
PIC16F872@SSOP28 [DX1026]
PIC16F873 [DX0001]
PIC16F873@SOIC28 [DX1033]
PIC16F873A [DX0001]
PIC16F873A(ISP)(Low-V) [DX0001]
PIC16F873A(ISP3.3v)(LV) [DX0001]

PIC16F873A@SOIC28(ISP3.3v)(HV) [DX0001]
PIC16F873A@SOIC28(ISP3.3v)(LV) [DX0001]
PIC16F873A@SSOP28 [DX1026]
PIC16F873A@SSOP28(ISP)(High-V) [DX0001]
PIC16F873A@SSOP28(ISP)(Low-V) [DX0001]
PIC16F873A@SSOP28(ISP3.3v)(HV) [DX0001]
PIC16F873A@SSOP28(ISP3.3v)(LV) [DX0001]
PIC16F874 [DX0001]
PIC16F874(ISP)
PIC16F874@MQFP44 [DX3088]
PIC16F874@MQFP44(ISP)
PIC16F874@PLCC44 [DX2044]
PIC16F874@PLCC44(ISP)
PIC16F874@TQFP44 [DX3003]
PIC16F874@TQFP44(ISP)
PIC16F874A [DX0001]
PIC16F874A(ISP)(High-V) [DX0001]
PIC16F874A(ISP)(Low-V) [DX0001]
PIC16F874A(ISP3.3v)(HV) [DX0001]
PIC16F874A(ISP3.3v)(LV) [DX0001]
PIC16F874A@PLCC44 [DX2044]
PIC16F874A@PLCC44(ISP)(High-V) [DX0001]
PIC16F874A@PLCC44(ISP)(Low-V) [DX0001]
PIC16F874A@PLCC44(ISP3.3v)(HV) [DX0001]
PIC16F874A@PLCC44(ISP3.3v)(LV) [DX0001]
PIC16F874A@TQFP44 [DX3003]
PIC16F874A@TQFP44(ISP)(High-V) [DX0001]
PIC16F874A@TQFP44(ISP)(Low-V) [DX0001]
PIC16F874A@TQFP44(ISP3.3v)(HV) [DX0001]
PIC16F874A@TQFP44(ISP3.3v)(LV) [DX0001]
PIC16F876 [DX0001]
PIC16F876(ISP)
PIC16F876@SOIC28 [DX1033]
PIC16F876@SOIC28(ISP)
PIC16F876A [DX0001]
PIC16F876A(ISP)(High-V) [DX0001]
PIC16F876A(ISP)(Low-V) [DX0001]
PIC16F876A(ISP3.3v)(HV) [DX0001]
PIC16F876A(ISP3.3v)(LV) [DX0001]
PIC16F876A@QFN28 [DX4014]
PIC16F876A@QFN28(ISP)(High-V) [DX0001]
PIC16F876A@QFN28(ISP)(Low-V) [DX0001]
PIC16F876A@QFN28(ISP3.3v)(HV) [DX0001]
PIC16F876A@QFN28(ISP3.3v)(LV) [DX0001]
PIC16F876A@SOIC28 [DX1033]
PIC16F876A@SOIC28(ISP)(High-V) [DX0001]
PIC16F876A@SOIC28(ISP)(Low-V) [DX0001]
PIC16F876A@SOIC28(ISP3.3v)(HV) [DX0001]
PIC16F876A@SOIC28(ISP3.3v)(LV) [DX0001]
PIC16F876A@SSOP28 [DX1026]
PIC16F876A@SSOP28(ISP)(High-V) [DX0001]
PIC16F876A@SSOP28(ISP)(Low-V) [DX0001]
PIC16F876A@SSOP28(ISP3.3v)(HV) [DX0001]
PIC16F876A@SSOP28(ISP3.3v)(LV) [DX0001]
PIC16F877 [DX0001]
PIC16F877(ISP)
PIC16F877@MQFP44 [DX3088]
PIC16F877@MQFP44(ISP)
PIC16F877@PLCC44 [DX2044]
PIC16F877@PLCC44(ISP)
PIC16F877@TQFP44 [DX3003]
PIC16F877@TQFP44(ISP)
PIC16F877A [DX0001]
PIC16F877A(ISP)(High-V) [DX0001]
PIC16F877A(ISP)(Low-V) [DX0001]
PIC16F877A(ISP3.3v)(HV) [DX0001]

PIC16F877A(ISP3.3v)(LV) [DX0001]　　PIC16F877A@PLCC44 [DX2044]
PIC16F877A@PLCC44(ISP)(High-V) [DX0001]
PIC16F877A@PLCC44(ISP)(Low-V) [DX0001]
PIC16F877A@PLCC44(ISP3.3v)(HV) [DX0001]
PIC16F877A@PLCC44(ISP3.3v)(LV) [DX0001]
PIC16F877A@TQFP44 [DX3003]
PIC16F877A@TQFP44(ISP)(High-V) [DX0001]
PIC16F877A@TQFP44(ISP)(Low-V) [DX0001]
PIC16F877A@TQFP44(ISP3.3v)(HV) [DX0001]
PIC16F877A@TQFP44(ISP3.3v)(LV) [DX0001]
PIC16F88 [DX0001]　　PIC16F88(ISP) [DX0001]
PIC16F88@QFN28 [DX4014]　　PIC16F88@QFN28(ISP) [DX0001]
PIC16F88@SOIC18 [DX1033]　　PIC16F88@SOIC18(ISP) [DX0001]
PIC16F88@SSOP20 [DX1026]　　PIC16F88@SSOP20(ISP) [DX0001]
PIC16F882 [DX0001]　　PIC16F882(ISP)(High-V) [DX0001]
PIC16F882(ISP)(Low-V) [DX0001]　　PIC16F882@QFN28 [DX4014]
PIC16F882@QFN28(ISP)(High-V) [DX0001]
PIC16F882@QFN28(ISP)(Low-V) [DX0001]
PIC16F882@SOIC28 [DX1033]
PIC16F882@SOIC28(ISP)(High-V) [DX0001]
PIC16F882@SOIC28(ISP)(Low-V) [DX0001]
PIC16F882@SSOP28 [DX1077]
PIC16F882@SSOP28(ISP)(High-V) [DX0001]
PIC16F882@SSOP28(ISP)(Low-V) [DX0001]
PIC16F883 [DX0001]　　PIC16F883(ISP)(High-V) [DX0001]
PIC16F883(ISP)(Low-V) [DX0001]　　PIC16F883@QFN28 [DX4014]
PIC16F883@QFN28(ISP)(High-V) [DX0001]
PIC16F883@QFN28(ISP)(Low-V) [DX0001]
PIC16F883@SOIC28 [DX1033]
PIC16F883@SOIC28(ISP)(High-V) [DX0001]
PIC16F883@SOIC28(ISP)(Low-V) [DX0001]
PIC16F883@SSOP28 [DX1077]
PIC16F883@SSOP28(ISP)(High-V) [DX0001]
PIC16F883@SSOP28(ISP)(Low-V) [DX0001]
PIC16F884 [DX0001]　　PIC16F884(ISP)(High-V) [DX0001]
PIC16F884(ISP)(Low-V) [DX0001]　　PIC16F884@QFN44 [DX4018]
PIC16F884@QFN44(ISP)(High-V) [DX0001]
PIC16F884@QFN44(ISP)(Low-V) [DX0001]
PIC16F884@QFN44(ML) [DX4019]
PIC16F884@QFN44(ML)(ISP)(High-V) [DX0001]
PIC16F884@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC16F884@TQFP44 [DX3003]
PIC16F884@TQFP44(ISP)(High-V) [DX0001]
PIC16F884@TQFP44(ISP)(Low-V) [DX0001]
PIC16F886 [DX0001]　　PIC16F886(ISP)(High-V) [DX0001]
PIC16F886(ISP)(Low-V) [DX0001]　　PIC16F886@QFN28 [DX4014]
PIC16F886@QFN28(ISP)(High-V) [DX0001]
PIC16F886@QFN28(ISP)(Low-V) [DX0001]

PIC16F886@SOIC28 [DX1033]
PIC16F886@SOIC28(ISP)(High-V) [DX0001]
PIC16F886@SOIC28(ISP)(Low-V) [DX0001]
PIC16F886@SSOP28 [DX1077]
PIC16F886@SSOP28(ISP)(High-V) [DX0001]
PIC16F886@SSOP28(ISP)(Low-V) [DX0001]
PIC16F887 [DX0001]
PIC16F887(ISP)(High-V) [DX0001]
PIC16F887(ISP)(Low-V) [DX0001]
PIC16F887@QFN44 [DX4018]
PIC16F887@QFN44(ISP)(High-V) [DX0001]
PIC16F887@QFN44(ISP)(Low-V) [DX0001]
PIC16F887@QFN44(ML) [DX4019]
PIC16F887@QFN44(ML)(ISP)(High-V) [DX0001]
PIC16F887@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC16F887@TQFP44 [DX3003]
PIC16F887@TQFP44(ISP)(High-V) [DX0001]
PIC16F887@TQFP44(ISP)(Low-V) [DX0001]
PIC16F913 [DX0001]
PIC16F913(ISP) [DX0001]
PIC16F913@QFN28 [DX4014]
PIC16F913@QFN28(ISP) [DX0001]
PIC16F913@SOIC28 [DX1033]
PIC16F913@SOIC28(ISP) [DX0001]
PIC16F913@SSOP28 [DX1026]
PIC16F913@SSOP28(ISP) [DX0001]
PIC16F914 [DX0001]
PIC16F914(ISP) [DX0001]
PIC16F914@QFN44 [DX4018]
PIC16F914@QFN44(ISP) [DX0001]
PIC16F914@QFN44(ML) [DX4019]
PIC16F914@QFN44(ML)(ISP) [DX0001]
PIC16F914@TQFP44 [DX3003]
PIC16F914@TQFP44(ISP) [DX0001]
PIC16F916 [DX0001]
PIC16F916(ISP) [DX0001]
PIC16F916@QFN28 [DX4014]
PIC16F916@QFN28(ISP) [DX0001]
PIC16F916@SOIC28 [DX1033]
PIC16F916@SOIC28(ISP) [DX0001]
PIC16F916@SSOP28 [DX1026]
PIC16F916@SSOP28(ISP) [DX0001]
PIC16F917 [DX0001]
PIC16F917(ISP) [DX0001]
PIC16F917@QFN44 [DX4018]
PIC16F917@QFN44(ISP) [DX0001]
PIC16F917@QFN44(ML) [DX4019]
PIC16F917@QFN44(ML)(ISP) [DX0001]
PIC16F917@TQFP44 [DX3003]
PIC16F917@TQFP44(ISP) [DX0001]
PIC16F946@TQFP64 [DX3011]
PIC16F946@TQFP64(ISP) [DX0001]
PIC16HV540 [DX0001]
PIC16HV540@SOIC18 [DX1033]
PIC16HV540@SSOP20 [DX1026]
PIC16HV610 [DX0001]
PIC16HV610(ISP) [DX0001]
PIC16HV610@QFN16 [DX4010]
PIC16HV610@QFN16(ISP) [DX0001]
PIC16HV610@SOIC14 [DX1016]
PIC16HV610@SOIC14(ISP) [DX0001]
PIC16HV610@TSSOP14 [DX1000]
PIC16HV610@TSSOP14(ISP) [DX0001]
PIC16HV616 [DX0001]
PIC16HV616(ISP) [DX0001]
PIC16HV616@QFN16 [DX4010]
PIC16HV616@QFN16(ISP) [DX0001]
PIC16HV616@SOIC14 [DX1016]
PIC16HV616@SOIC14(ISP) [DX0001]
PIC16HV616@TSSOP14 [DX1000]
PIC16HV616@TSSOP14(ISP) [DX0001]
PIC16HV753 [DX0001]
PIC16HV753(ISP) [DX0001]
PIC16HV753@SOIC14 [DX1016]
PIC16HV753@TSSOP14 [DX1073]
PIC16HV785 [DX0001]
PIC16HV785(ISP) [DX0001]
PIC16HV785@QFN20 [DX4011]

PIC16HV785@QFN20(ISP) [DX0001]
PIC16HV785@SOIC20(ISP) [DX0001]
PIC16HV785@SSOP20(ISP) [DX0001]
PIC16LC505@SOIC14 [DX1016]
PIC16LC54A@SOIC18 [DX1033]
PIC16LC54C [DX0001]
PIC16LC54C@SSOP20 [DX1026]
PIC16LC554(ISP) [DX0001]
PIC16LC554@SOIC18(ISP) [DX0001]
PIC16LC558(ISP) [DX0001]
PIC16LC558@SOIC18(ISP) [DX0001]
PIC16LC56A@SOIC18 [DX1033]
PIC16LC58A [DX0001]
PIC16LC58A@SSOP20 [DX1026]
PIC16LC58B@SOIC18 [DX1033]
PIC16LC620 [DX0001]
PIC16LC620@SOIC18 [DX1033]
PIC16LC620A [DX0001]
PIC16LC620A@SOIC18 [DX1033]
PIC16LC620A@SSOP20 [DX1026]
PIC16LC621A [DX0001]
PIC16LC621A@SOIC18 [DX1033]
PIC16LC621A@SSOP20 [DX1026]
PIC16LC622 [DX0001]
PIC16LC622@SOIC18 [DX1033]
PIC16LC62A [DX0001]
PIC16LC62A@SOIC28 [DX1033]
PIC16LC62A@SSOP28 [DX1026]
PIC16LC62B [DX0001]
PIC16LC62B@SOIC28 [DX1033]
PIC16LC62B@SSOP28 [DX1026]
PIC16LC63 [DX0001]
PIC16LC63@SOIC28 [DX1033]
PIC16LC63A [DX0001]
PIC16LC63A@SOIC28 [DX1033]
PIC16LC63A@SSOP28 [DX1026]
PIC16LC64A [DX0001]
PIC16LC64A@PLCC44 [DX2044]
PIC16LC64A@TQFP44 [DX3003]
PIC16LC65A [DX0001]
PIC16LC65A@PLCC44 [DX2044]
PIC16LC65A@TQFP44 [DX3003]
PIC16LC65B [DX0001]
PIC16LC65B@PLCC44 [DX2044]
PIC16LC65B@TQFP44 [DX3003]
PIC16LC66 [DX0001]
PIC16LC66@SOIC28 [DX1033]
PIC16LC67 [DX0001]
PIC16HV785@SOIC20 [DX1033]
PIC16HV785@SSOP20 [DX1026]
PIC16LC505 [DX0001]
PIC16LC54A [DX0001]
PIC16LC54A@SSOP20 [DX1026]
PIC16LC54C@SOIC18 [DX1033]
PIC16LC554 [DX0001]
PIC16LC554@SOIC18 [DX1033]
PIC16LC558 [DX0001]
PIC16LC558@SOIC18 [DX1033]
PIC16LC56A [DX0001]
PIC16LC56A@SSOP20 [DX1026]
PIC16LC58A@SOIC18 [DX1033]
PIC16LC58B [DX0001]
PIC16LC58B@SSOP20 [DX1026]
PIC16LC620(ISP) [DX0001]
PIC16LC620@SOIC18(ISP) [DX0001]
PIC16LC620A(ISP) [DX0001]
PIC16LC620A@SOIC18(ISP) [DX0001]
PIC16LC620A@SSOP20(ISP) [DX0001]
PIC16LC621A(ISP) [DX0001]
PIC16LC621A@SOIC18(ISP) [DX0001]
PIC16LC621A@SSOP20(ISP) [DX0001]
PIC16LC622(ISP) [DX0001]
PIC16LC622@SOIC18(ISP) [DX0001]
PIC16LC62A(ISP) [DX0001]
PIC16LC62A@SOIC28(ISP) [DX0001]
PIC16LC62A@SSOP28(ISP) [DX0001]
PIC16LC62B(ISP) [DX0001]
PIC16LC62B@SOIC28(ISP) [DX0001]
PIC16LC62B@SSOP28(ISP) [DX0001]
PIC16LC63(ISP) [DX0001]
PIC16LC63@SOIC28(ISP) [DX0001]
PIC16LC63A(ISP) [DX0001]
PIC16LC63A@SOIC28(ISP) [DX0001]
PIC16LC63A@SSOP28(ISP) [DX0001]
PIC16LC64A(ISP) [DX0001]
PIC16LC64A@PLCC44(ISP) [DX0001]
PIC16LC64A@TQFP44(ISP) [DX0001]
PIC16LC65A(ISP) [DX0001]
PIC16LC65A@PLCC44(ISP) [DX0001]
PIC16LC65A@TQFP44(ISP) [DX0001]
PIC16LC65B(ISP) [DX0001]
PIC16LC65B@PLCC44(ISP) [DX0001]
PIC16LC65B@TQFP44(ISP) [DX0001]
PIC16LC66(ISP) [DX0001]
PIC16LC66@SOIC28(ISP) [DX0001]
PIC16LC67(ISP) [DX0001]

PIC16LC67@PLCC44 [DX2044]
PIC16LC67@TQFP44 [DX3003]
PIC16LC71 [DX0001]
PIC16LC71@SOIC18 [DX1033]
PIC16LC710 [DX0001]
PIC16LC710@SOIC18 [DX1033]
PIC16LC710@SSOP20 [DX1026]
PIC16LC711 [DX0001]
PIC16LC711@SOIC18 [DX1033]
PIC16LC711@SSOP20 [DX1026]
PIC16LC712 [DX0001]
PIC16LC712@SOIC18 [DX1033]
PIC16LC712@SSOP20 [DX1026]
PIC16LC715 [DX0001]
PIC16LC716 [DX0001]
PIC16LC716@SOIC18 [DX1033]
PIC16LC716@SSOP20 [DX1026]
PIC16LC717 [DX0001]
PIC16LC717@SOIC18 [DX1033]
PIC16LC717@SSOP20 [DX1026]
PIC16LC72 [DX0001]
PIC16LC72@SOIC28 [DX1033]
PIC16LC72@SSOP28 [DX1026]
PIC16LC72A [DX0001]
PIC16LC72A@SOIC28 [DX1033]
PIC16LC72A@SSOP28 [DX1026]
PIC16LC73A [DX0001]
PIC16LC73A@SOIC28 [DX1033]
PIC16LC73B [DX0001]
PIC16LC73B@SOIC28 [DX1033]
PIC16LC73B@SSOP28 [DX1026]
PIC16LC74 [DX0001]
PIC16LC74@PLCC44 [DX2044]
PIC16LC74@TQFP44 [DX3003]
PIC16LC74A [DX0001]
PIC16LC74A@PLCC44 [DX2044]
PIC16LC74A@TQFP44 [DX3003]
PIC16LC74B [DX0001]
PIC16LC74B@MQFP44 [DX3002]
PIC16LC74B@PLCC44 [DX2044]
PIC16LC74B@TQFP44 [DX3003]
PIC16LC76 [DX0001]
PIC16LC76@SOIC28 [DX1033]
PIC16LC77 [DX0001]
PIC16LC77@PLCC44 [DX2044]
PIC16LC773 [DX0001]
PIC16LC773@SOIC28 [DX1033]
PIC16LC773@SSOP28 [DX1026]

PIC16LC67@PLCC44(ISP) [DX0001]
PIC16LC67@TQFP44(ISP) [DX0001]
PIC16LC71(ISP) [DX0001]
PIC16LC71@SOIC18(ISP) [DX0001]
PIC16LC710(ISP) [DX0001]
PIC16LC710@SOIC18(ISP) [DX0001]
PIC16LC710@SSOP20(ISP) [DX0001]
PIC16LC711(ISP) [DX0001]
PIC16LC711@SOIC18(ISP) [DX0001]
PIC16LC711@SSOP20(ISP) [DX0001]
PIC16LC712(ISP) [DX0001]
PIC16LC712@SOIC18(ISP) [DX0001]
PIC16LC712@SSOP20(ISP) [DX0001]
PIC16LC715@SOIC18 [DX1033]
PIC16LC716(ISP) [DX0001]
PIC16LC716@SOIC18(ISP) [DX0001]
PIC16LC716@SSOP20(ISP) [DX0001]
PIC16LC717(ISP) [DX0001]
PIC16LC717@SOIC18(ISP) [DX0001]
PIC16LC717@SSOP20(ISP) [DX0001]
PIC16LC72(ISP) [DX0001]
PIC16LC72@SOIC28(ISP) [DX0001]
PIC16LC72@SSOP28(ISP) [DX0001]
PIC16LC72A(ISP) [DX0001]
PIC16LC72A@SOIC28(ISP) [DX0001]
PIC16LC72A@SSOP28(ISP) [DX0001]
PIC16LC73A(ISP) [DX0001]
PIC16LC73A@SOIC28(ISP) [DX0001]
PIC16LC73B(ISP) [DX0001]
PIC16LC73B@SOIC28(ISP) [DX0001]
PIC16LC73B@SSOP28(ISP) [DX0001]
PIC16LC74(ISP) [DX0001]
PIC16LC74@PLCC44(ISP) [DX0001]
PIC16LC74@TQFP44(ISP) [DX0001]
PIC16LC74A(ISP) [DX0001]
PIC16LC74A@PLCC44(ISP) [DX0001]
PIC16LC74A@TQFP44(ISP) [DX0001]
PIC16LC74B(ISP) [DX0001]
PIC16LC74B@MQFP44(ISP) [DX0001]
PIC16LC74B@PLCC44(ISP) [DX0001]
PIC16LC74B@TQFP44(ISP) [DX0001]
PIC16LC76(ISP) [DX0001]
PIC16LC76@SOIC28(ISP) [DX0001]
PIC16LC77(ISP) [DX0001]
PIC16LC77@PLCC44(ISP) [DX0001]
PIC16LC773(ISP) [DX0001]
PIC16LC773@SOIC28(ISP) [DX0001]
PIC16LC773@SSOP28(ISP) [DX0001]

PIC16LC774 [DX0001]
PIC16LC774@PLCC44 [DX2044]
PIC16LC774@TQFP44 [DX3003]
PIC16LC84 [DX0001]
PIC16LC84@SOIC18 [DX1033]
PIC16LC923@PLCC68 [DX2068]
PIC16LC923@SDIP64 [DX0064]
PIC16LC923@TQFP64 [DX3011]
PIC16LC924@PLCC68 [DX2068]
PIC16LC924@SDIP64 [DX0064]
PIC16LC924@TQFP64 [DX3011]
PIC16LC925@PLCC68 [DX2068]
PIC16LC925@TQFP64 [DX3011]
PIC16LC926@PLCC68 [DX2068]
PIC16LC926@TQFP64 [DX3011]
PIC16LCE623@SOIC18 [DX1033]
PIC16LCE623@SSOP20 [DX1026]
PIC16LF1454 [DX0001]
PIC16LF1454@QFN16 [DX4010]
PIC16LF1454@TSSOP14 [DX1000]
PIC16LF1455(ISP) [DX0001]
PIC16LF1455@SOIC14 [DX1016]
PIC16LF1458 [DX0001]
PIC16LF1458@QFN20 [DX4011]
PIC16LF1458@SSOP20 [DX1026]
PIC16LF1459(ISP) [DX0001]
PIC16LF1459@SOIC20 [DX1033]
PIC16LF1503 [DX0001]
PIC16LF1503@QFN16 [DX4053]
PIC16LF1503@SOIC14 [DX1016]
PIC16LF1503@TSSOP14 [DX1073]
PIC16LF1503@TSSOP14(ISP) [DX0001]
PIC16LF1507 [DX0001]
PIC16LF1507@QFN20 [DX4011]
PIC16LF1507@SOIC20 [DX1033]
PIC16LF1507@SSOP20 [DX1070A]
PIC16LF1508 [DX0001]
PIC16LF1508@QFN20 [DX4011]
PIC16LF1508@SOIC20 [DX1033]
PIC16LF1508@SSOP20 [DX1070A]
PIC16LF1509 [DX0001]
PIC16LF1509@QFN20 [DX4011]
PIC16LF1509@SOIC20 [DX1033]
PIC16LF1509@SSOP20 [DX1070A]
PIC16LF1512 [DX0001]
PIC16LF1512@SOIC28 [DX1033]
PIC16LF1512@SSOP28 [DX1077]
PIC16LF1512@UQFN28 [DX4036]

PIC16LC774(ISP) [DX0001]
PIC16LC774@PLCC44(ISP) [DX0001]
PIC16LC774@TQFP44(ISP) [DX0001]
PIC16LC84(ISP) [DX0001]
PIC16LC84@SOIC18(ISP) [DX0001]
PIC16LC923@PLCC68(ISP) [DX0001]
PIC16LC923@SDIP64(ISP) [DX0001]
PIC16LC923@TQFP64(ISP) [DX0001]
PIC16LC924@PLCC68(ISP) [DX0001]
PIC16LC924@SDIP64(ISP) [DX0001]
PIC16LC924@TQFP64(ISP) [DX0001]
PIC16LC925@PLCC68(ISP) [DX0001]
PIC16LC925@TQFP64(ISP) [DX0001]
PIC16LC926@PLCC68(ISP) [DX0001]
PIC16LC926@TQFP64(ISP) [DX0001]
PIC16LCE623@SOIC18(ISP) [DX0001]
PIC16LCE623@SSOP20(ISP) [DX0001]
PIC16LF1454(ISP) [DX0001]
PIC16LF1454@SOIC14 [DX1016]
PIC16LF1455 [DX0001]
PIC16LF1455@QFN16 [DX4010]
PIC16LF1455@TSSOP14 [DX1000]
PIC16LF1458(ISP) [DX0001]
PIC16LF1458@SOIC20 [DX1033]
PIC16LF1459 [DX0001]
PIC16LF1459@QFN20 [DX4011]
PIC16LF1459@SSOP20 [DX1026]
PIC16LF1503(ISP) [DX0001]
PIC16LF1503@QFN16(ISP) [DX0001]
PIC16LF1503@SOIC14(ISP) [DX0001]

PIC16LF1507(ISP) [DX0001]
PIC16LF1507@QFN20(ISP) [DX0001]
PIC16LF1507@SOIC20(ISP) [DX0001]
PIC16LF1507@SSOP20(ISP) [DX0001]
PIC16LF1508(ISP) [DX0001]
PIC16LF1508@QFN20(ISP) [DX0001]
PIC16LF1508@SOIC20(ISP) [DX0001]
PIC16LF1508@SSOP20(ISP) [DX0001]
PIC16LF1509(ISP) [DX0001]
PIC16LF1509@QFN20(ISP) [DX0001]
PIC16LF1509@SOIC20(ISP) [DX0001]
PIC16LF1509@SSOP20(ISP) [DX0001]
PIC16LF1512(ISP) [DX0001]
PIC16LF1512@SOIC28(ISP) [DX0001]
PIC16LF1512@SSOP28(ISP) [DX0001]
PIC16LF1512@UQFN28(ISP) [DX0001]

PIC16LF1513 [DX0001]
PIC16LF1513@SOIC28 [DX1033]
PIC16LF1513@SSOP28 [DX1077]
PIC16LF1513@UQFN28 [DX4036]
PIC16LF1516 [DX0001]
PIC16LF1516@SOIC28 [DX1033]
PIC16LF1516@SSOP28 [DX1077]
PIC16LF1516@UQFN28 [DX4036]
PIC16LF1517 [DX0001]
PIC16LF1517@TQFP44 [DX3003]
PIC16LF1517@UQFN40 [DX4039]
PIC16LF1518 [DX0001]
PIC16LF1518@SOIC28 [DX1033]
PIC16LF1518@SSOP28 [DX1077]
PIC16LF1518@UQFN28 [DX4036]
PIC16LF1519 [DX0001]
PIC16LF1519@TQFP44 [DX3003]
PIC16LF1519@UQFN40 [DX4039]
PIC16LF1526@QFN64 [DX3011]
PIC16LF1526@TQFP64 [DX3011]
PIC16LF1527@QFN64 [DX3011]
PIC16LF1527@TQFP64 [DX3011]
PIC16LF1554 [DX0001]
PIC16LF1554@QFN16 [DX4053]
PIC16LF1554@TSSOP14 [DX1073]
PIC16LF1559@ISP [DX0001]
PIC16LF1559@SOIC20 [DX1033]
PIC16LF1574 [DX0001]
PIC16LF1574-Q16 [DX4053]
PIC16LF1574-T14 [DX1000]
PIC16LF1575@ISP [DX0001]
PIC16LF1575-S14 [DX1016]
PIC16LF1578 [DX0001]
PIC16LF1578-Q20 [DX4011]
PIC16LF1578-SS20 [DX1070]
PIC16LF1579@ISP [DX0001]
PIC16LF1579-S20 [DX1033]
PIC16LF1703 [DX0001]
PIC16LF1703@QFN16 [DX4053]
PIC16LF1703@TSSOP14 [DX1000]
PIC16LF1704@ISP [DX0001]
PIC16LF1704@SOIC14 [DX1016]
PIC16LF1705 [DX0001]
PIC16LF1705@QFN16 [DX4053]
PIC16LF1705@TSSOP14 [DX1000]
PIC16LF1707@ISP [DX0001]
PIC16LF1707@SOIC20 [DX1033]
PIC16LF1708 [DX0001]
PIC16LF1513(ISP) [DX0001]
PIC16LF1513@SOIC28(ISP) [DX0001]
PIC16LF1513@SSOP28(ISP) [DX0001]
PIC16LF1513@UQFN28(ISP) [DX0001]
PIC16LF1516(ISP) [DX0001]
PIC16LF1516@SOIC28(ISP) [DX0001]
PIC16LF1516@SSOP28(ISP) [DX0001]
PIC16LF1516@UQFN28(ISP) [DX0001]
PIC16LF1517(ISP) [DX0001]
PIC16LF1517@TQFP44(ISP) [DX0001]
PIC16LF1517@UQFN40(ISP) [DX0001]
PIC16LF1518(ISP) [DX0001]
PIC16LF1518@SOIC28(ISP) [DX0001]
PIC16LF1518@SSOP28(ISP) [DX0001]
PIC16LF1518@UQFN28(ISP) [DX0001]
PIC16LF1519(ISP) [DX0001]
PIC16LF1519@TQFP44(ISP) [DX0001]
PIC16LF1519@UQFN40(ISP) [DX0001]
PIC16LF1526@QFN64(ISP) [DX0001]
PIC16LF1526@TQFP64(ISP) [DX0001]
PIC16LF1527@QFN64(ISP) [DX0001]
PIC16LF1527@TQFP64(ISP) [DX0001]
PIC16LF1554@ISP [DX0001]
PIC16LF1554@SOIC14 [DX1016]
PIC16LF1559 [DX0001]
PIC16LF1559@QFN20 [DX4011]
PIC16LF1559@SSOP20 [DX1026]
PIC16LF1574@ISP [DX0001]
PIC16LF1574-S14 [DX1016]
PIC16LF1575 [DX0001]
PIC16LF1575-Q16 [DX4053]
PIC16LF1575-T14 [DX1000]
PIC16LF1578@ISP [DX0001]
PIC16LF1578-S20 [DX1033]
PIC16LF1579 [DX0001]
PIC16LF1579-Q20 [DX4011]
PIC16LF1579-SS20 [DX1070]
PIC16LF1703@ISP [DX0001]
PIC16LF1703@SOIC14 [DX1016]
PIC16LF1704 [DX0001]
PIC16LF1704@QFN16 [DX4053]
PIC16LF1704@TSSOP14 [DX1000]
PIC16LF1705@ISP [DX0001]
PIC16LF1705@SOIC14 [DX1016]
PIC16LF1707 [DX0001]
PIC16LF1707@QFN20 [DX4011]
PIC16LF1707@SSOP20 [DX1070]
PIC16LF1708@ISP [DX0001]

PIC16LF1708@QFN20 [DX4011]
PIC16LF1708@SOIC20 [DX1033]
PIC16LF1708@SSOP20 [DX1070]
PIC16LF1709 [DX0001]
PIC16LF1709@ISP [DX0001]
PIC16LF1709@QFN20 [DX4011]
PIC16LF1709@SOIC20 [DX1033]
PIC16LF1709@SSOP20 [DX1070]
PIC16LF1782 [DX0001]
PIC16LF1782(ISP) [DX0001]
PIC16LF1782@SOIC28 [DX1033]
PIC16LF1782@SOIC28(ISP) [DX0001]
PIC16LF1782@SSOP28 [DX1026]
PIC16LF1782@SSOP28(ISP) [DX0001]
PIC16LF1782@UQFN28 [DX4014]
PIC16LF1782@UQFN28(ISP) [DX0001]
PIC16LF1783 [DX0001]
PIC16LF1783(ISP) [DX0001]
PIC16LF1783@SOIC28 [DX1033]
PIC16LF1783@SOIC28(ISP) [DX0001]
PIC16LF1783@SSOP28 [DX1026]
PIC16LF1783@SSOP28(ISP) [DX0001]
PIC16LF1783@UQFN28 [DX4014]
PIC16LF1783@UQFN28(ISP) [DX0001]
PIC16LF1784 [DX0001]
PIC16LF1784(ISP) [DX0001]
PIC16LF1784@QFN44 [DX4019]
PIC16LF1784@TQFP44 [DX3003]
PIC16LF1784@UQFN40
PIC16LF1786 [DX0001]
PIC16LF1786(ISP) [DX0001]
PIC16LF1786@QFN28 [DX4014]
PIC16LF1786@SOIC28 [DX1033]
PIC16LF1786@SSOP28 [DX1026]
PIC16LF1787 [DX0001]
PIC16LF1787(ISP) [DX0001]
PIC16LF1787@QFN44 [DX4019]
PIC16LF1787@TQFP44 [DX3003]
PIC16LF1787@UQFN40
PIC16LF1788 [DX0001]
PIC16LF1788(ISP) [DX0001]
PIC16LF1788@QFN28 [DX4014]
PIC16LF1788@SOIC28 [DX1033]
PIC16LF1788@SSOP28 [DX1026]
PIC16LF1789 [DX0001]
PIC16LF1789(ISP) [DX0001]
PIC16LF1789@QFN44 [DX4019]
PIC16LF1789@TQFP44 [DX3003]
PIC16LF1789@UQFN40
PIC16LF1823 [DX0001]
PIC16LF1823(8-word) [DX0001]
PIC16LF1823(ISP)(HV) [DX0001]
PIC16LF1823(LV) [DX0001]
PIC16LF1823(LVISP) [DX0001]
PIC16LF1823@QFN16(3*3) [DX4008]
PIC16LF1823@QFN16(3*3)(8-word) [DX4008]
PIC16LF1823@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16LF1823@QFN16(3*3)(LV) [DX4008]
PIC16LF1823@QFN16(4*4) [DX4010]
PIC16LF1823@QFN16(4*4)(8-word) [DX4010]
PIC16LF1823@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16LF1823@QFN16(4*4)(LV) [DX4010]
PIC16LF1823@SOIC14 [DX1016]
PIC16LF1823@SOIC14(8-word) [DX1016]
PIC16LF1823@SOIC14(ISP)(HV) [DX0001]
PIC16LF1823@SOIC14(LV) [DX1016]
PIC16LF1823@TSSOP14 [DX1073]
PIC16LF1823@TSSOP14(8-word) [DX1073]
PIC16LF1823@TSSOP14(ISP)(HV) [DX0001]
PIC16LF1823@TSSOP14(LV) [DX1000]
PIC16LF1824 [DX0001]
PIC16LF1824(8-word) [DX0001]
PIC16LF1824(ISP)(HV) [DX0001]
PIC16LF1824(LV) [DX0001]
PIC16LF1824(LVISP) [DX0001]
PIC16LF1824@QFN16(3*3) [DX4008]
PIC16LF1824@QFN16(3*3)(8-word) [DX4008]
PIC16LF1824@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16LF1824@QFN16(3*3)(LV) [DX4008]

PIC16LF1824@QFN16(4*4) [DX4010]
PIC16LF1824@QFN16(4*4)(8-word) [DX4010]
PIC16LF1824@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16LF1824@QFN16(4*4)(LV) [DX4010]
PIC16LF1824@SOIC14 [DX1016]
PIC16LF1824@SOIC14(8-word) [DX1016]
PIC16LF1824@SOIC14(ISP)(HV) [DX0001]
PIC16LF1824@SOIC14(LV) [DX1016]
PIC16LF1824@TSSOP14 [DX1073]
PIC16LF1824@TSSOP14(8-word) [DX1073]
PIC16LF1824@TSSOP14(ISP)(HV) [DX0001]
PIC16LF1824@TSSOP14(LV) [DX1000]
PIC16LF1825 [DX0001]
PIC16LF1825(8-word) [DX0001]
PIC16LF1825(ISP)(HV) [DX0001]
PIC16LF1825(LV) [DX0001]
PIC16LF1825(LVISP) [DX0001]
PIC16LF1825@QFN16(3*3) [DX4008]
PIC16LF1825@QFN16(3*3)(8-word) [DX4008]
PIC16LF1825@QFN16(3*3)(ISP)(HV) [DX0001]
PIC16LF1825@QFN16(3*3)(LV) [DX4008]
PIC16LF1825@QFN16(4*4) [DX4010]
PIC16LF1825@QFN16(4*4)(8-word) [DX4010]
PIC16LF1825@QFN16(4*4)(ISP)(HV) [DX0001]
PIC16LF1825@QFN16(4*4)(LV) [DX4010]
PIC16LF1825@SOIC14 [DX1016]
PIC16LF1825@SOIC14(8-word) [DX1016]
PIC16LF1825@SOIC14(ISP)(HV) [DX0001]
PIC16LF1825@SOIC14(LV) [DX1016]
PIC16LF1825@TSSOP14 [DX1073]
PIC16LF1825@TSSOP14(8-word) [DX1073]
PIC16LF1825@TSSOP14(ISP)(HV) [DX0001]
PIC16LF1825@TSSOP14(LV) [DX1000]
PIC16LF1826 [DX0001]
PIC16LF1826(8-word) [DX0001]
PIC16LF1826(ISP)(HV) [DX0001]
PIC16LF1826(LV) [DX0001]
PIC16LF1826(LVISP) [DX0001]
PIC16LF1826@QFN28 [DX4014]
PIC16LF1826@QFN28(8-word) [DX4014]
PIC16LF1826@QFN28(ISP)(HV) [DX0001]
PIC16LF1826@QFN28(LV) [DX4014]
PIC16LF1826@SOIC18 [DX1033]
PIC16LF1826@SOIC18(8-word) [DX1033]
PIC16LF1826@SOIC18(ISP)(HV) [DX0001]
PIC16LF1826@SOIC18(LV) [DX1033]
PIC16LF1826@SSOP20 [DX1070]
PIC16LF1826@SSOP20(8-word) [DX1070]
PIC16LF1826@SSOP20(ISP)(HV) [DX0001]
PIC16LF1826@SSOP20(LV) [DX1026]
PIC16LF1826@UQFN28 [DX4036]
PIC16LF1826@UQFN28(8-word) [DX4036]
PIC16LF1827 [DX0001]
PIC16LF1827(8-word) [DX0001]
PIC16LF1827(ISP)(HV) [DX0001]
PIC16LF1827(LV) [DX0001]
PIC16LF1827(LVISP) [DX0001]
PIC16LF1827@QFN28 [DX4014]
PIC16LF1827@QFN28(8-word) [DX4014]
PIC16LF1827@QFN28(ISP)(HV) [DX0001]
PIC16LF1827@QFN28(LV) [DX4014]
PIC16LF1827@SOIC18 [DX1033]
PIC16LF1827@SOIC18(8-word) [DX1033]

PIC16LF1827@SOIC18(ISP)(HV) [DX0001]
PIC16LF1827@SOIC18(LV) [DX1033] PIC16LF1827@SSOP20 [DX1070]
PIC16LF1827@SSOP20(8-word) [DX1070]
PIC16LF1827@SSOP20(ISP)(HV) [DX0001]
PIC16LF1827@SSOP20(LV) [DX1026] PIC16LF1827@UQFN28 [DX4036]
PIC16LF1827@UQFN28(8-word) [DX4036]
PIC16LF1828 [DX0001] PIC16LF1828(8-word) [DX0001]
PIC16LF1828(ISP)(HV) [DX0001] PIC16LF1828(LV) [DX0001]
PIC16LF1828(LVISP) [DX0001] PIC16LF1828@QFN20 [DX4011]
PIC16LF1828@QFN20(8-word) [DX4011]
PIC16LF1828@QFN20(ISP)(HV) [DX0001]
PIC16LF1828@QFN20(LV) [DX4011] PIC16LF1828@SOIC20 [DX1033]
PIC16LF1828@SOIC20(8-word) [DX1033]
PIC16LF1828@SOIC20(ISP)(HV) [DX0001]
PIC16LF1828@SOIC20(LV) [DX1033] PIC16LF1828@TSSOP20 [DX1070]
PIC16LF1828@TSSOP20(8-word) [DX1070]
PIC16LF1828@TSSOP20(ISP)(HV) [DX0001]
PIC16LF1828@TSSOP20(LV) [DX1026] PIC16LF1829 [DX0001]
PIC16LF1829(8-word) [DX0001] PIC16LF1829(ISP)(HV) [DX0001]
PIC16LF1829(LV) [DX0001] PIC16LF1829(LVISP) [DX0001]
PIC16LF1829@QFN20 [DX4011]
PIC16LF1829@QFN20(8-word) [DX4011]
PIC16LF1829@QFN20(ISP)(HV) [DX0001]
PIC16LF1829@QFN20(LV) [DX4011] PIC16LF1829@SOIC20 [DX1033]
PIC16LF1829@SOIC20(8-word) [DX1033]
PIC16LF1829@SOIC20(ISP)(HV) [DX0001]
PIC16LF1829@SOIC20(LV) [DX1033] PIC16LF1829@TSSOP20 [DX1070]
PIC16LF1829@TSSOP20(8-word) [DX1070]
PIC16LF1829@TSSOP20(ISP)(HV) [DX0001]
PIC16LF1829@TSSOP20(LV) [DX1026] PIC16LF1847 [DX0001]
PIC16LF1847(ISP)(HV) [DX0001] PIC16LF1847@QFN28 [DX4014]
PIC16LF1847@QFN28(ISP)(HV) [DX0001]
PIC16LF1847@SOIC18 [DX1033]
PIC16LF1847@SOIC18(ISP)(HV) [DX0001]
PIC16LF1847@SSOP20 [DX1026]
PIC16LF1847@SSOP20(ISP)(HV) [DX0001]
PIC16LF1847E [DX0001] PIC16LF1847E@QFN28 [DX4014]
PIC16LF1847E@SOIC18 [DX1033] PIC16LF1847E@SSOP20 [DX1026]
PIC16LF1902 [DX0001] PIC16LF1902(ISP)(HV) [DX0001]
PIC16LF1902@QFN28 [DX4014]
PIC16LF1902@QFN28(ISP)(HV) [DX0001]
PIC16LF1902@QFN28[8-word pro] [DX4014]
PIC16LF1902@SOIC28 [DX1033]
PIC16LF1902@SOIC28(ISP)(HV) [DX0001]
PIC16LF1902@SOIC28[8-word pro] [DX1033]
PIC16LF1902@SSOP28 [DX1026]
PIC16LF1902@SSOP28(ISP)(HV) [DX0001]
PIC16LF1902@SSOP28[8-word pro] [DX1026]

PIC16LF1902[8-word pro] [DX0001]　　PIC16LF1903 [DX0001]
PIC16LF1903(ISP)(HV) [DX0001]　　PIC16LF1903@QFN28 [DX4014]
PIC16LF1903@QFN28(ISP)(HV) [DX0001]
PIC16LF1903@QFN28[8-word pro] [DX4014]
PIC16LF1903@SOIC28 [DX1033]
PIC16LF1903@SOIC28(ISP)(HV) [DX0001]
PIC16LF1903@SOIC28[8-word pro] [DX1033]
PIC16LF1903@SSOP28 [DX1026]
PIC16LF1903@SSOP28(ISP)(HV) [DX0001]
PIC16LF1903@SSOP28[8-word pro] [DX1026]
PIC16LF1903[8-word pro] [DX0001]　　PIC16LF1904 [DX0001]
PIC16LF1904(ISP)(HV) [DX0001]　　PIC16LF1904@TQFP44 [DX3003]
PIC16LF1904@TQFP44(ISP)(HV) [DX0001]
PIC16LF1904@TQFP44[8-word pro] [DX3003]
PIC16LF1904@UQFN40 [DX4039]
PIC16LF1904@UQFN40(ISP)(HV) [DX0001]
PIC16LF1904@UQFN40[8-word pro] [DX4039]
PIC16LF1904[8-word pro] [DX0001]　　PIC16LF1906 [DX0001]
PIC16LF1906(ISP)(HV) [DX0001]　　PIC16LF1906@QFN28 [DX4014]
PIC16LF1906@QFN28(ISP)(HV) [DX0001]
PIC16LF1906@QFN28[8-word pro] [DX4014]
PIC16LF1906@SOIC28 [DX1033]
PIC16LF1906@SOIC28(ISP)(HV) [DX0001]
PIC16LF1906@SOIC28[8-word pro] [DX1033]
PIC16LF1906@SSOP28 [DX1026]
PIC16LF1906@SSOP28(ISP)(HV) [DX0001]
PIC16LF1906@SSOP28[8-word pro] [DX1026]
PIC16LF1906[8-word pro] [DX0001]　　PIC16LF1907 [DX0001]
PIC16LF1907(ISP)(HV) [DX0001]　　PIC16LF1907@TQFP44 [DX3003]
PIC16LF1907@TQFP44(ISP)(HV) [DX0001]
PIC16LF1907@TQFP44[8-word pro] [DX3003]
PIC16LF1907@UQFN40 [DX4039]
PIC16LF1907@UQFN40(ISP)(HV) [DX0001]
PIC16LF1907@UQFN40[8-word pro] [DX4039]
PIC16LF1907[8-word pro] [DX0001]　　PIC16LF1933 [DX0001]
PIC16LF1933(ISP)(HV) [DX0001]　　PIC16LF1933@QFN28 [DX4014]
PIC16LF1933@QFN28(ISP)(HV) [DX0001]
PIC16LF1933@QFN28[8-word pro] [DX4014]
PIC16LF1933@SOIC28 [DX1033]
PIC16LF1933@SOIC28(ISP)(HV) [DX0001]
PIC16LF1933@SOIC28[8-word pro] [DX1033]
PIC16LF1933@SSOP28 [DX1077]
PIC16LF1933@SSOP28(ISP)(HV) [DX0001]
PIC16LF1933@SSOP28[8-word pro] [DX1077]
PIC16LF1933@UQFN28 [DX4036]　　PIC16LF1933[8-word pro] [DX0001]
PIC16LF1934 [DX0001]　　PIC16LF1934(ISP)(HV) [DX0001]
PIC16LF1934@QFN44 [DX4019]
PIC16LF1934@QFN44(ISP)(HV) [DX0001]

PIC16LF1934@QFN44[8-word pro] [DX4019]
PIC16LF1934@TQFP44 [DX3003]
PIC16LF1934@TQFP44(ISP)(HV) [DX0001]
PIC16LF1934@TQFP44[8-word pro] [DX3003]
PIC16LF1934[8-word pro] [DX0001]　　PIC16LF1936 [DX0001]
PIC16LF1936(ISP)(HV) [DX0001]　　PIC16LF1936@QFN28 [DX4014]
PIC16LF1936@QFN28(ISP)(HV) [DX0001]
PIC16LF1936@QFN28[8-word pro] [DX4014]
PIC16LF1936@SOIC28 [DX1033]
PIC16LF1936@SOIC28(ISP)(HV) [DX0001]
PIC16LF1936@SOIC28[8-word pro] [DX1033]
PIC16LF1936@SSOP28 [DX1077]
PIC16LF1936@SSOP28(ISP)(HV) [DX0001]
PIC16LF1936@SSOP28[8-word pro] [DX1077]
PIC16LF1936@UQFN28 [DX4036]　　PIC16LF1936[8-word pro] [DX0001]
PIC16LF1937 [DX0001]　　PIC16LF1937(ISP)(HV) [DX0001]
PIC16LF1937@QFN44 [DX4019]
PIC16LF1937@QFN44(ISP)(HV) [DX0001]
PIC16LF1937@QFN44[8-word pro] [DX4019]
PIC16LF1937@TQFP44 [DX3003]
PIC16LF1937@TQFP44(ISP)(HV) [DX0001]
PIC16LF1937@TQFP44[8-word pro] [DX3003]
PIC16LF1937[8-word pro] [DX0001]　　PIC16LF1938 [DX0001]
PIC16LF1938(ISP)(HV) [DX0001]　　PIC16LF1938@QFN28 [DX4014]
PIC16LF1938@QFN28(ISP)(HV) [DX0001]
PIC16LF1938@QFN28[8-word pro] [DX4014]
PIC16LF1938@SOIC28 [DX1033]
PIC16LF1938@SOIC28(ISP)(HV) [DX0001]
PIC16LF1938@SOIC28[8-word pro] [DX1033]
PIC16LF1938@SSOP28 [DX1077]
PIC16LF1938@SSOP28(ISP)(HV) [DX0001]
PIC16LF1938@SSOP28[8-word pro] [DX1077]
PIC16LF1938@UQFN28 [DX4036]　　PIC16LF1938[8-word pro] [DX0001]
PIC16LF1939 [DX0001]　　PIC16LF1939(ISP)(HV) [DX0001]
PIC16LF1939@QFN44 [DX4019]
PIC16LF1939@QFN44(ISP)(HV) [DX0001]
PIC16LF1939@QFN44[8-word pro] [DX4019]
PIC16LF1939@TQFP44 [DX3003]
PIC16LF1939@TQFP44(ISP)(HV) [DX0001]
PIC16LF1939@TQFP44[8-word pro] [DX3003]
PIC16LF1939[8-word pro] [DX0001]　　PIC16LF1946@QFN64 [DX4023]
PIC16LF1946@QFN64(ISP)(HV) [DX0001]
PIC16LF1946@QFN64[8-word pro] [DX4023]
PIC16LF1946@TQFP64 [DX3011]
PIC16LF1946@TQFP64(ISP)(HV) [DX0001]
PIC16LF1946@TQFP64[8-word pro] [DX3011]
PIC16LF1947@QFN64 [DX4023]
PIC16LF1947@QFN64(ISP)(HV) [DX0001]

PIC16LF1947@QFN64[8-word pro] [DX4023]
PIC16LF1947@TQFP64 [DX3011]
PIC16LF1947@TQFP64(ISP)(HV) [DX0001]
PIC16LF1947@TQFP64[8-word pro] [DX3011]

PIC16LF505 [DX0001]	PIC16LF505(ISP) [DX0001]
PIC16LF505@SOIC14 [DX1065]	PIC16LF505@SOIC14(ISP) [DX0001]
PIC16LF505@TSSOP14 [DX1000]	PIC16LF505@TSSOP14(ISP) [DX0001]
PIC16LF506 [DX0001]	PIC16LF506(ISP) [DX0001]
PIC16LF506@SOIC14 [DX1030]	PIC16LF506@SOIC14(ISP) [DX0001]
PIC16LF506@TSSOP14 [DX1001]	PIC16LF506@TSSOP14(ISP) [DX0001]
PIC16LF526 [DX0001]	PIC16LF526(ISP) [DX0001]
PIC16LF526@SOIC14 [DX1016]	PIC16LF526@SOIC14(ISP) [DX0001]
PIC16LF526@TSSOP14 [DX1000]	PIC16LF526@TSSOP14(ISP) [DX0001]
PIC16LF54 [DX0001]	PIC16LF54(ISP) [DX0001]
PIC16LF54@SOIC18 [DX1033]	PIC16LF54@SOIC18(ISP) [DX0001]
PIC16LF54@SSOP20 [DX1026]	PIC16LF54@SSOP20(ISP) [DX0001]
PIC16LF57 [DX0001]	PIC16LF57(ISP) [DX0001]
PIC16LF57@SOIC28 [DX1033]	PIC16LF57@SOIC28(ISP) [DX0001]
PIC16LF57@SSOP28 [DX1026]	PIC16LF57@SSOP28(ISP) [DX0001]
PIC16LF59 [DX0001]	PIC16LF59(ISP) [DX0001]
PIC16LF59@PLCC44 [DX2044]	PIC16LF59@PLCC44(ISP) [DX0001]
PIC16LF59@TQFP44 [DX3003]	PIC16LF59@TQFP44(ISP) [DX0001]
PIC16LF627 [DX0001]	PIC16LF627(ISP) [DX0001]
PIC16LF627@SOIC18 [DX1033]	PIC16LF627@SOIC18(ISP) [DX0001]
PIC16LF627@SSOP20 [DX1026]	PIC16LF627@SSOP20(ISP) [DX0001]
PIC16LF627A [DX0001]	PIC16LF627A(ISP) [DX0001]
PIC16LF627A@SOIC18 [DX1033]	PIC16LF627A@SOIC18(ISP) [DX0001]
PIC16LF627A@SSOP20 [DX1026]	PIC16LF627A@SSOP20(ISP) [DX0001]
PIC16LF628 [DX0001]	PIC16LF628(ISP) [DX0001]
PIC16LF628@SOIC18 [DX1033]	PIC16LF628@SOIC18(ISP) [DX0001]
PIC16LF628@SSOP20 [DX1026]	PIC16LF628@SSOP20(ISP) [DX0001]
PIC16LF628A [DX0001]	PIC16LF628A(ISP) [DX0001]
PIC16LF628A@SOIC18 [DX1033]	PIC16LF628A@SOIC18(ISP) [DX0001]
PIC16LF628A@SSOP20 [DX1026]	PIC16LF628A@SSOP20(ISP) [DX0001]
PIC16LF631 [DX0001]	PIC16LF631(ISP) [DX0001]
PIC16LF631@QFN20 [DX4011]	PIC16LF631@QFN20(ISP) [DX0001]
PIC16LF631@SOIC20 [DX1033]	PIC16LF631@SOIC20(ISP) [DX0001]
PIC16LF631@SSOP20 [DX1070]	PIC16LF631@SSOP20(ISP) [DX0001]
PIC16LF639 [DX0001]	PIC16LF639(ISP) [DX0001]
PIC16LF639@QFN20 [DX4011]	PIC16LF639@QFN20(ISP) [DX0001]
PIC16LF639@SOIC20 [DX1033]	PIC16LF639@SOIC20(ISP) [DX0001]
PIC16LF639@SSOP20 [DX1070]	PIC16LF639@SSOP20(ISP) [DX0001]
PIC16LF648A [DX0001]	PIC16LF648A(ISP) [DX0001]
PIC16LF648A@SOIC18 [DX1033]	PIC16LF648A@SOIC18(ISP) [DX0001]
PIC16LF648A@SSOP20 [DX1026]	PIC16LF648A@SSOP20(ISP) [DX0001]
PIC16LF677 [DX0001]	PIC16LF677(ISP) [DX0001]
PIC16LF677@QFN20 [DX4011]	PIC16LF677@QFN20(ISP) [DX0001]
PIC16LF677@SOIC20 [DX1033]	PIC16LF677@SOIC20(ISP) [DX0001]

PIC16LF677@SSOP20 [DX1070]
PIC16LF677@SSOP20(ISP) [DX0001]
PIC16LF685 [DX0001]
PIC16LF685(ISP) [DX0001]
PIC16LF685@QFN20 [DX4011]
PIC16LF685@QFN20(ISP) [DX0001]
PIC16LF685@SOIC20 [DX1033]
PIC16LF685@SOIC20(ISP) [DX0001]
PIC16LF685@SSOP20 [DX1070]
PIC16LF685@SSOP20(ISP) [DX0001]
PIC16LF687 [DX0001]
PIC16LF687(ISP) [DX0001]
PIC16LF687@QFN20 [DX4011]
PIC16LF687@QFN20(ISP) [DX0001]
PIC16LF687@SOIC20 [DX1033]
PIC16LF687@SOIC20(ISP) [DX0001]
PIC16LF687@SSOP20 [DX1070]
PIC16LF687@SSOP20(ISP) [DX0001]
PIC16LF689 [DX0001]
PIC16LF689(ISP) [DX0001]
PIC16LF689@QFN20 [DX4011]
PIC16LF689@QFN20(ISP) [DX0001]
PIC16LF689@SOIC20 [DX1033]
PIC16LF689@SOIC20(ISP) [DX0001]
PIC16LF689@SSOP20 [DX1070]
PIC16LF689@SSOP20(ISP) [DX0001]
PIC16LF690 [DX0001]
PIC16LF690(ISP) [DX0001]
PIC16LF690@QFN20 [DX4011]
PIC16LF690@QFN20(ISP) [DX0001]
PIC16LF690@SOIC20 [DX1033]
PIC16LF690@SOIC20(ISP) [DX0001]
PIC16LF690@SSOP20 [DX1070]
PIC16LF690@SSOP20(ISP) [DX0001]
PIC16LF707 [DX0001]
PIC16LF707(ISP) [DX0001]
PIC16LF707@QFN44 [DX4019]
PIC16LF707@QFN44(ISP) [DX0001]
PIC16LF707@TQFP44 [DX3003]
PIC16LF707@TQFP44(ISP) [DX0001]
PIC16LF716 [DX0001]
PIC16LF716(4-WORD PRO) [DX0001]
PIC16LF716(ISP) [DX0001]
PIC16LF716@SOIC18 [DX1033]
PIC16LF716@SOIC18(4-WORD PRO) [DX1033]
PIC16LF716@SOIC18(ISP) [DX0001]
PIC16LF716@SSOP20 [DX1026]
PIC16LF716@SSOP20(4-WORD PRO) [DX1026]
PIC16LF716@SSOP20(ISP) [DX0001]
PIC16LF72 [DX0001]
PIC16LF72(ISP) [DX0001]
PIC16LF72@QFN28 [DX4014]
PIC16LF72@QFN28(ISP) [DX0001]
PIC16LF72@SOIC28 [DX1033]
PIC16LF72@SOIC28(ISP) [DX0001]
PIC16LF72@SSOP28 [DX1026]
PIC16LF72@SSOP28(ISP) [DX0001]
PIC16LF720 [DX0001]
PIC16LF720@QFN20 [DX4011]
PIC16LF720@SOIC20 [DX1033]
PIC16LF720@SSOP20 [DX1026]
PIC16LF721 [DX0001]
PIC16LF721@QFN20 [DX4011]
PIC16LF721@SOIC20 [DX1033]
PIC16LF721@SSOP20 [DX1026]
PIC16LF722 [DX0001]
PIC16LF722(ISP) [DX0001]
PIC16LF722@QFN28 [DX4014]
PIC16LF722@QFN28(ISP) [DX0001]
PIC16LF722@SOIC28 [DX1033]
PIC16LF722@SOIC28(ISP) [DX0001]
PIC16LF722@SSOP28 [DX1077]
PIC16LF722@SSOP28(ISP) [DX0001]
PIC16LF722A [DX0001]
PIC16LF722A(ISP) [DX0001]
PIC16LF722A@QFN28 [DX4014]
PIC16LF722A@QFN28(ISP) [DX0001]
PIC16LF722A@SOIC28 [DX1033]
PIC16LF722A@SOIC28(ISP) [DX0001]
PIC16LF722A@SSOP28 [DX1077]
PIC16LF722A@SSOP28(ISP) [DX0001]
PIC16LF723 [DX0001]
PIC16LF723(ISP) [DX0001]
PIC16LF723@QFN28 [DX4014]
PIC16LF723@QFN28(ISP) [DX0001]
PIC16LF723@SOIC28 [DX1033]
PIC16LF723@SOIC28(ISP) [DX0001]
PIC16LF723@SSOP28 [DX1077]
PIC16LF723@SSOP28(ISP) [DX0001]
PIC16LF723A [DX0001]
PIC16LF723A(ISP) [DX0001]
PIC16LF723A@QFN28 [DX4014]
PIC16LF723A@QFN28(ISP) [DX0001]
PIC16LF723A@SOIC28 [DX1033]

PIC16LF723A@SOIC28(ISP) [DX0001]
PIC16LF723A@SSOP28(ISP) [DX0001]
PIC16LF724(ISP) [DX0001]
PIC16LF724@QFN44(ISP) [DX0001]
PIC16LF724@TQFP44(ISP) [DX0001]
PIC16LF726(ISP) [DX0001]
PIC16LF726@QFN28(ISP) [DX0001]
PIC16LF726@SOIC28(ISP) [DX0001]
PIC16LF726@SSOP28(ISP) [DX0001]
PIC16LF727(ISP) [DX0001]
PIC16LF727@QFN44(ISP) [DX0001]
PIC16LF727@TQFP44(ISP) [DX0001]
PIC16LF73(ISP) [DX0001]
PIC16LF73@SOIC28 [DX1033]
PIC16LF73@SSOP28 [DX1026]
PIC16LF737 [DX0001]
PIC16LF737@SOIC28 [DX1033]
PIC16LF737@SSOP28 [DX1077]
PIC16LF74 [DX0001]
PIC16LF74@PLCC44 [DX2044]
PIC16LF74@TQFP44 [DX3003]
PIC16LF747 [DX0001]
PIC16LF747@TQFP44 [DX3003]
PIC16LF76 [DX0001]
PIC16LF76@QFN28 [DX4014]
PIC16LF76@SOIC28(ISP) [DX0001]
PIC16LF76@SSOP28(ISP) [DX0001]
PIC16LF767(ISP) [DX0001]
PIC16LF767@SOIC28(ISP) [DX0001]
PIC16LF767@SSOP28(ISP) [DX0001]
PIC16LF77(ISP) [DX0001]
PIC16LF77@PLCC44(ISP) [DX0001]
PIC16LF77@TQFP44(ISP) [DX0001]
PIC16LF777(ISP) [DX0001]
PIC16LF777@TQFP44(ISP) [DX0001]
PIC16LF818(ISP) [DX0001]
PIC16LF818@QFN28(ISP) [DX0001]
PIC16LF818@SOIC18(ISP) [DX0001]
PIC16LF818@SSOP20(ISP) [DX0001]
PIC16LF819(ISP) [DX0001]
PIC16LF819@QFN28(ISP) [DX0001]
PIC16LF819@SOIC18(ISP) [DX0001]
PIC16LF819@SSOP20(ISP) [DX0001]
PIC16LF83(ISP) [DX0001]
PIC16LF83@SOIC18(ISP) [DX0001]
PIC16LF84(ISP) [DX0001]
PIC16LF84@SOIC18(ISP) [DX0001]
PIC16LF84A(ISP) [DX0001]
PIC16LF723A@SSOP28 [DX1077]
PIC16LF724 [DX0001]
PIC16LF724@QFN44 [DX4019]
PIC16LF724@TQFP44 [DX3003]
PIC16LF726 [DX0001]
PIC16LF726@QFN28 [DX4014]
PIC16LF726@SOIC28 [DX1033]
PIC16LF726@SSOP28 [DX1077]
PIC16LF727 [DX0001]
PIC16LF727@QFN44 [DX4019]
PIC16LF727@TQFP44 [DX3003]
PIC16LF73 [DX0001]
PIC16LF73@QFN28 [DX4014]
PIC16LF73@SOIC28(ISP) [DX0001]
PIC16LF73@SSOP28(ISP) [DX0001]
PIC16LF737(ISP) [DX0001]
PIC16LF737@SOIC28(ISP) [DX0001]
PIC16LF737@SSOP28(ISP) [DX0001]
PIC16LF74(ISP) [DX0001]
PIC16LF74@PLCC44(ISP) [DX0001]
PIC16LF74@TQFP44(ISP) [DX0001]
PIC16LF747(ISP) [DX0001]
PIC16LF747@TQFP44(ISP) [DX0001]
PIC16LF76(ISP) [DX0001]
PIC16LF76@SOIC28 [DX1033]
PIC16LF76@SSOP28 [DX1026]
PIC16LF767 [DX0001]
PIC16LF767@SOIC28 [DX1033]
PIC16LF767@SSOP28 [DX1077]
PIC16LF77 [DX0001]
PIC16LF77@PLCC44 [DX2044]
PIC16LF77@TQFP44 [DX3003]
PIC16LF777 [DX0001]
PIC16LF777@TQFP44 [DX3003]
PIC16LF818 [DX0001]
PIC16LF818@QFN28 [DX4014]
PIC16LF818@SOIC18 [DX1033]
PIC16LF818@SSOP20 [DX1026]
PIC16LF819 [DX0001]
PIC16LF819@QFN28 [DX4014]
PIC16LF819@SOIC18 [DX1033]
PIC16LF819@SSOP20 [DX1026]
PIC16LF83 [DX0001]
PIC16LF83@SOIC18 [DX1033]
PIC16LF84 [DX0001]
PIC16LF84@SOIC18 [DX1033]
PIC16LF84A [DX0001]
PIC16LF84A@SOIC18 [DX1033]

PIC16LF84A@SOIC18(ISP) [DX0001]
PIC16LF84A@SSOP20(ISP) [DX0001]
PIC16LF87(ISP) [DX0001]
PIC16LF87@QFN28(ISP) [DX0001]
PIC16LF87@SOIC18(ISP) [DX0001]
PIC16LF87@SSOP20(ISP) [DX0001]
PIC16LF870(ISP)
PIC16LF870@SOIC28(ISP)
PIC16LF870@SSOP28(ISP)
PIC16LF871(ISP)
PIC16LF871@MQFP44(ISP)
PIC16LF871@PLCC44(ISP)
PIC16LF871@TQFP44(ISP)
PIC16LF872(ISP)
PIC16LF872@SOIC28(ISP)
PIC16LF872@SSOP28(ISP)
PIC16LF873(ISP)
PIC16LF873@SOIC28(ISP)
PIC16LF84A@SSOP20 [DX1026]
PIC16LF87 [DX0001]
PIC16LF87@QFN28 [DX4014]
PIC16LF87@SOIC18 [DX1033]
PIC16LF87@SSOP20 [DX1026]
PIC16LF870 [DX0001]
PIC16LF870@SOIC28 [DX1033]
PIC16LF870@SSOP28 [DX1026]
PIC16LF871 [DX0001]
PIC16LF871@MQFP44 [DX3088]
PIC16LF871@PLCC44 [DX2044]
PIC16LF871@TQFP44 [DX3003]
PIC16LF872 [DX0001]
PIC16LF872@SOIC28 [DX1033]
PIC16LF872@SSOP28 [DX1026]
PIC16LF873 [DX0001]
PIC16LF873@SOIC28 [DX1033]
PIC16LF873A [DX0001]
PIC16LF873A(ISP)(High-V) [DX0001]
PIC16LF873A(ISP)(Low-V) [DX0001]
PIC16LF873A(ISP3.3v)(HV) [DX0001]
PIC16LF873A(ISP3.3v)(LV) [DX0001]
PIC16LF873A@QFN28 [DX4014]
PIC16LF873A@QFN28(ISP)(High-V) [DX0001]
PIC16LF873A@QFN28(ISP)(Low-V) [DX0001]
PIC16LF873A@QFN28(ISP3.3v)(HV) [DX0001]
PIC16LF873A@QFN28(ISP3.3v)(LV) [DX0001]
PIC16LF873A@SOIC28 [DX1033]
PIC16LF873A@SOIC28(ISP)(High-V) [DX0001]
PIC16LF873A@SOIC28(ISP)(Low-V) [DX0001]
PIC16LF873A@SOIC28(ISP3.3v)(HV) [DX0001]
PIC16LF873A@SOIC28(ISP3.3v)(LV) [DX0001]
PIC16LF873A@SSOP28 [DX1026]
PIC16LF873A@SSOP28(ISP)(High-V) [DX0001]
PIC16LF873A@SSOP28(ISP)(Low-V) [DX0001]
PIC16LF873A@SSOP28(ISP3.3v)(HV) [DX0001]
PIC16LF873A@SSOP28(ISP3.3v)(LV) [DX0001]
PIC16LF874 [DX0001]
PIC16LF874@MQFP44 [DX3088]
PIC16LF874@PLCC44 [DX2044]
PIC16LF874@TQFP44 [DX3003]
PIC16LF874(ISP)
PIC16LF874@MQFP44(ISP)
PIC16LF874@PLCC44(ISP)
PIC16LF874@TQFP44(ISP)
PIC16LF874A [DX0001]
PIC16LF874A(ISP)(High-V) [DX0001]
PIC16LF874A(ISP)(Low-V) [DX0001]
PIC16LF874A(ISP3.3v)(HV) [DX0001]
PIC16LF874A(ISP3.3v)(LV) [DX0001]
PIC16LF874A@PLCC44 [DX2044]
PIC16LF874A@PLCC44(ISP)(High-V) [DX0001]

PIC16LF874A@PLCC44(ISP)(Low-V) [DX0001]
PIC16LF874A@PLCC44(ISP3.3v)(HV) [DX0001]
PIC16LF874A@PLCC44(ISP3.3v)(LV) [DX0001]
PIC16LF874A@TQFP44 [DX3003]
PIC16LF874A@TQFP44(ISP)(High-V) [DX0001]
PIC16LF874A@TQFP44(ISP)(Low-V) [DX0001]
PIC16LF874A@TQFP44(ISP3.3v)(HV) [DX0001]
PIC16LF874A@TQFP44(ISP3.3v)(LV) [DX0001]
PIC16LF876 [DX0001]
PIC16LF876(ISP)
PIC16LF876@SOIC28 [DX1033]
PIC16LF876@SOIC28(ISP)
PIC16LF876A [DX0001]
PIC16LF876A(ISP)(High-V) [DX0001]
PIC16LF876A(ISP)(Low-V) [DX0001]
PIC16LF876A(ISP3.3v)(HV) [DX0001]
PIC16LF876A(ISP3.3v)(LV) [DX0001]
PIC16LF876A@QFN28 [DX4014]
PIC16LF876A@QFN28(ISP)(High-V) [DX0001]
PIC16LF876A@QFN28(ISP)(Low-V) [DX0001]
PIC16LF876A@QFN28(ISP3.3v)(HV) [DX0001]
PIC16LF876A@QFN28(ISP3.3v)(LV) [DX0001]
PIC16LF876A@SOIC28 [DX1033]
PIC16LF876A@SOIC28(ISP)(High-V) [DX0001]
PIC16LF876A@SOIC28(ISP)(Low-V) [DX0001]
PIC16LF876A@SOIC28(ISP3.3v)(HV) [DX0001]
PIC16LF876A@SOIC28(ISP3.3v)(LV) [DX0001]
PIC16LF876A@SSOP28 [DX1026]
PIC16LF876A@SSOP28(ISP)(High-V) [DX0001]
PIC16LF876A@SSOP28(ISP)(Low-V) [DX0001]
PIC16LF876A@SSOP28(ISP3.3v)(HV) [DX0001]
PIC16LF876A@SSOP28(ISP3.3v)(LV) [DX0001]
PIC16LF877 [DX0001]
PIC16LF877(ISP)
PIC16LF877@MQFP44 [DX3088]
PIC16LF877@MQFP44(ISP)
PIC16LF877@PLCC44 [DX2044]
PIC16LF877@PLCC44(ISP)
PIC16LF877@TQFP44 [DX3003]
PIC16LF877@TQFP44(ISP)
PIC16LF877A [DX0001]
PIC16LF877A(ISP)(High-V) [DX0001]
PIC16LF877A(ISP)(Low-V) [DX0001]
PIC16LF877A(ISP3.3v)(HV) [DX0001]
PIC16LF877A(ISP3.3v)(LV) [DX0001]
PIC16LF877A@PLCC44 [DX2044]
PIC16LF877A@PLCC44(ISP)(High-V) [DX0001]
PIC16LF877A@PLCC44(ISP)(Low-V) [DX0001]
PIC16LF877A@PLCC44(ISP3.3v)(HV) [DX0001]
PIC16LF877A@PLCC44(ISP3.3v)(LV) [DX0001]
PIC16LF877A@TQFP44 [DX3003]
PIC16LF877A@TQFP44(ISP)(High-V) [DX0001]
PIC16LF877A@TQFP44(ISP)(Low-V) [DX0001]
PIC16LF877A@TQFP44(ISP3.3v)(HV) [DX0001]

PIC16LF877A@TQFP44(ISP3.3v)(LV) [DX0001]
PIC16LF88 [DX0001]
PIC16LF88(ISP) [DX0001]
PIC16LF88@QFN28 [DX4014]
PIC16LF88@QFN28(ISP) [DX0001]
PIC16LF88@SOIC18 [DX1033]
PIC16LF88@SOIC18(ISP) [DX0001]
PIC16LF88@SSOP20 [DX1026]
PIC16LF88@SSOP20(ISP) [DX0001]
PIC16LF913 [DX0001]
PIC16LF913(ISP) [DX0001]
PIC16LF913@QFN28 [DX4014]
PIC16LF913@QFN28(ISP) [DX0001]
PIC16LF913@SOIC28 [DX1033]
PIC16LF913@SOIC28(ISP) [DX0001]
PIC16LF913@SSOP28 [DX1026]
PIC16LF913@SSOP28(ISP) [DX0001]
PIC16LF914 [DX0001]
PIC16LF914(ISP) [DX0001]
PIC16LF914@QFN44 [DX4018]
PIC16LF914@QFN44(ISP) [DX0001]
PIC16LF914@QFN44(ML) [DX4019]
PIC16LF914@QFN44(ML)(ISP) [DX0001]
PIC16LF914@TQFP44 [DX3003]
PIC16LF914@TQFP44(ISP) [DX0001]
PIC16LF916 [DX0001]
PIC16LF916(ISP) [DX0001]
PIC16LF916@QFN28 [DX4014]
PIC16LF916@QFN28(ISP) [DX0001]
PIC16LF916@SOIC28 [DX1033]
PIC16LF916@SOIC28(ISP) [DX0001]
PIC16LF916@SSOP28 [DX1026]
PIC16LF916@SSOP28(ISP) [DX0001]
PIC16LF917 [DX0001]
PIC16LF917(ISP) [DX0001]
PIC16LF917@QFN44 [DX4018]
PIC16LF917@QFN44(ISP) [DX0001]
PIC16LF917@QFN44(ML) [DX4019]
PIC16LF917@QFN44(ML)(ISP) [DX0001]
PIC16LF917@TQFP44 [DX3003]
PIC16LF917@TQFP44(ISP) [DX0001]
PIC16LF946@TQFP64 [DX3011]
PIC16LF946@TQFP64(ISP) [DX0001]
PIC16LV54A [DX0001]
PIC16LV54A@SOIC18 [DX1033]
PIC16LV54A@SSOP20 [DX1026]
PIC16LV58A [DX0001]
PIC16LV58A@SOIC18 [DX1033]
PIC16LV58A@SSOP20 [DX1026]
PIC17C42 [DX0001]
PIC17C42@PLCC44 [DX2044]
PIC17C42@TQFP44 [DX3003]
PIC17C42A [DX0001]
PIC17C42A@PLCC44 [DX2044]
PIC17C42A@TQFP44 [DX3003]
PIC17C43 [DX0001]
PIC17C43@PLCC44 [DX2044]
PIC17C43@TQFP44 [DX3003]
PIC17C44 [DX0001]
PIC17C44@PLCC44 [DX2044]
PIC17C44@TQFP44 [DX3003]
PIC17C752@PLCC68 [DX2068]
PIC17C752@TQFP64 [DX3011]
PIC17C756@PLCC68 [DX2068]
PIC17C756@TQFP64 [DX3011]
PIC17C756A@PLCC68 [DX2068]
PIC17C756A@TQFP64 [DX3011]
PIC17C762@PLCC84 [DX2084]
PIC17C766@PLCC84 [DX2084]
PIC17LC42 [DX0001]
PIC17LC42@PLCC44 [DX2044]
PIC17LC42@TQFP44 [DX3003]
PIC17LC42A [DX0001]
PIC17LC42A@PLCC44 [DX2044]
PIC17LC42A@TQFP44 [DX3003]
PIC17LC43 [DX0001]
PIC17LC43@PLCC44 [DX2044]
PIC17LC43@TQFP44 [DX3003]
PIC17LC44 [DX0001]
PIC17LC44@PLCC44 [DX2044]
PIC17LC44@TQFP44 [DX3003]
PIC17LC752@PLCC68 [DX2068]
PIC17LC752@TQFP64 [DX3011]
PIC17LC756@PLCC68 [DX2068]
PIC17LC756@TQFP64 [DX3011]
PIC17LC756A@PLCC68 [DX2068]
PIC17LC756A@TQFP64 [DX3011]
PIC17LC762@PLCC84 [DX2084]
PIC17LC766@PLCC84 [DX2084]
PIC18C242 [DX0001]
PIC18C242@SOIC28 [DX1033]

PIC18C252 [DX0001]
PIC18C252@SOIC28 [DX1033]
PIC18C442 [DX0001]
PIC18C442@PLCC44 [DX2044]
PIC18C442@TQFP44 [DX3003]
PIC18C452 [DX0001]
PIC18C452@PLCC44 [DX2044]
PIC18C452@TQFP44 [DX3003]
PIC18C658@PLCC68 [DX2068]
PIC18C658@TQFP64 [DX3011]
PIC18C858@PLCC84 [DX2084]
PIC18C858@TQFP80 [DX3016]
PIC18F1220 [DX0001]
PIC18F1220(ISP) [DX0001]
PIC18F1220@QFN28 [DX4014]
PIC18F1220@SOIC18 [DX1033]
PIC18F1220@SOIC18(ISP) [DX0001]
PIC18F1220@SSOP20 [DX1026]
PIC18F1220@SSOP20(ISP) [DX0001]
PIC18F1230 [DX0001]
PIC18F1230(ISP) [DX0001]
PIC18F1230@QFN28 [DX4014]
PIC18F1230@QFN28(ISP) [DX0001]
PIC18F1230@SOIC18 [DX1033]
PIC18F1230@SOIC18(ISP) [DX0001]
PIC18F1230@SSOP20 [DX1026]
PIC18F1230@SSOP20(ISP) [DX0001]
PIC18F1320 [DX0001]
PIC18F1320(ISP) [DX0001]
PIC18F1320@QFN28 [DX4014]
PIC18F1320@SOIC18 [DX1033]
PIC18F1320@SOIC18(ISP) [DX0001]
PIC18F1320@SSOP20 [DX1026]
PIC18F1320@SSOP20(ISP) [DX0001]
PIC18F1330 [DX0001]
PIC18F1330(ISP) [DX0001]
PIC18F1330@QFN28 [DX4014]
PIC18F1330@QFN28(ISP) [DX0001]
PIC18F1330@SOIC18 [DX1033]
PIC18F1330@SOIC18(ISP) [DX0001]
PIC18F1330@SSOP20 [DX1026]
PIC18F1330@SSOP20(ISP) [DX0001]
PIC18F1330-ICD@QFN28 [DX4014]
PIC18F1330-ICD@QFN28(ISP) [DX0001]
PIC18F13K22 [DX0001]
PIC18F13K22(ISP)(High-V) [DX0001]
PIC18F13K22(ISP)(Low-V) [DX0001]
PIC18F13K22@QFN20 [DX4011]
PIC18F13K22@QFN20(ISP)(High-V) [DX0001]
PIC18F13K22@QFN20(ISP)(Low-V) [DX0001]
PIC18F13K22@SOIC20 [DX1033]
PIC18F13K22@SOIC20(ISP)(High-V) [DX0001]
PIC18F13K22@SOIC20(ISP)(Low-V) [DX0001]
PIC18F13K22@SSOP20 [DX1026]
PIC18F13K22@SSOP20(ISP)(High-V) [DX0001]
PIC18F13K22@SSOP20(ISP)(Low-V) [DX0001]
PIC18F13K50 [DX0001]
PIC18F13K50(ISP)(High-V) [DX0001]
PIC18F13K50(ISP)(Low-V) [DX0001]
PIC18F13K50@QFN20 [DX4025]
PIC18F13K50@QFN20(ISP)(High-V) [DX0001]
PIC18F13K50@QFN20(ISP)(Low-V) [DX0001]
PIC18F13K50@SOIC20 [DX1033]
PIC18F13K50@SOIC20(ISP)(High-V) [DX0001]
PIC18F13K50@SOIC20(ISP)(Low-V) [DX0001]
PIC18F13K50@SSOP20 [DX1026]
PIC18F13K50@SSOP20(ISP)(High-V) [DX0001]
PIC18F13K50@SSOP20(ISP)(Low-V) [DX0001]
PIC18F14K22 [DX0001]
PIC18F14K22(ISP)(High-V) [DX0001]
PIC18F14K22(ISP)(Low-V) [DX0001]
PIC18F14K22@QFN20 [DX4011]

PIC18F14K22@QFN20(ISP)(High-V) [DX0001]
PIC18F14K22@QFN20(ISP)(Low-V) [DX0001]
PIC18F14K22@SOIC20 [DX1033]
PIC18F14K22@SOIC20(ISP)(High-V) [DX0001]
PIC18F14K22@SOIC20(ISP)(Low-V) [DX0001]
PIC18F14K22@SSOP20 [DX1026]
PIC18F14K22@SSOP20(ISP)(High-V) [DX0001]
PIC18F14K22@SSOP20(ISP)(Low-V) [DX0001]
PIC18F14K50 [DX0001]
PIC18F14K50(ISP)(High-V) [DX0001]
PIC18F14K50(ISP)(Low-V) [DX0001] PIC18F14K50@QFN20 [DX4025]
PIC18F14K50@QFN20(ISP)(High-V) [DX0001]
PIC18F14K50@QFN20(ISP)(Low-V) [DX0001]
PIC18F14K50@SOIC20 [DX1033]
PIC18F14K50@SOIC20(ISP)(High-V) [DX0001]
PIC18F14K50@SOIC20(ISP)(Low-V) [DX0001]
PIC18F14K50@SSOP20 [DX1026]
PIC18F14K50@SSOP20(ISP)(High-V) [DX0001]
PIC18F14K50@SSOP20(ISP)(Low-V) [DX0001]
PIC18F2220 [DX0001] PIC18F2220(ISP) [DX0001]
PIC18F2220@SOIC28 [DX1033] PIC18F2220@SOIC28(ISP) [DX0001]
PIC18F2221 [DX0001] PIC18F2221(ISP)(Low-V) [DX0001]
PIC18F2221@QFN28 [DX4014]
PIC18F2221@QFN28(ISP)(Low-V) [DX0001]
PIC18F2221@SOIC28 [DX1033]
PIC18F2221@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2221@SSOP28 [DX1026]
PIC18F2221@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2320 [DX0001] PIC18F2320(ISP) [DX0001]
PIC18F2320@SOIC28 [DX1033] PIC18F2320@SOIC28(ISP) [DX0001]
PIC18F2321 [DX0001] PIC18F2321(ISP)(Low-V) [DX0001]
PIC18F2321@QFN28 [DX4014]
PIC18F2321@QFN28(ISP)(Low-V) [DX0001]
PIC18F2321@SOIC28 [DX1033]
PIC18F2321@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2321@SSOP28 [DX1026]
PIC18F2321@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2331 [DX0001] PIC18F2331(ISP) [DX0001]
PIC18F2331@SOIC28 [DX1033] PIC18F2331@SOIC28(ISP) [DX0001]
PIC18F23K20 [DX0001]
PIC18F23K20(ISP)(High-V) [DX0001]
PIC18F23K20(ISP)(Low-V) [DX0001] PIC18F23K20@QFN28 [DX4014]
PIC18F23K20@QFN28(ISP)(High-V) [DX0001]
PIC18F23K20@QFN28(ISP)(Low-V) [DX0001]
PIC18F23K20@SOIC28 [DX1033]
PIC18F23K20@SOIC28(ISP)(High-V) [DX0001]
PIC18F23K20@SOIC28(ISP)(Low-V) [DX0001]
PIC18F23K20@SSOP28 [DX1077]

PIC18F23K20@SSOP28(ISP)(High-V) [DX0001]
PIC18F23K20@SSOP28(ISP)(Low-V) [DX0001]
PIC18F23K20@UQFN28 [DX4036]
PIC18F23K22 [DX0001]
PIC18F23K22(ISP)(H-V) [DX0001]
PIC18F23K22@QFN28 [DX4014]
PIC18F23K22@QFN28(ISP)(H-V) [DX0001]
PIC18F23K22@SOIC28 [DX1033]
PIC18F23K22@SOIC28(ISP)(H-V) [DX0001]
PIC18F23K22@SSOP28 [DX1077]
PIC18F23K22@SSOP28(ISP)(H-V) [DX0001]
PIC18F23K22@UQFN28 [DX4036]
PIC18F2410 [DX0001]
PIC18F2410(ISP)(Low-V) [DX0001]
PIC18F2410@QFN28 [DX4014]
PIC18F2410@QFN28(ISP)(Low-V) [DX0001]
PIC18F2410@SOIC28 [DX1033]
PIC18F2410@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2410@SSOP28 [DX1026]
PIC18F2410@SSOP28(ISP)(Low-V) [DX0001]
PIC18F242 [DX0001]
PIC18F242(ISP) [DX0001]
PIC18F242@SOIC28 [DX1033]
PIC18F242@SOIC28(ISP) [DX0001]
PIC18F2420 [DX0001]
PIC18F2420(ISP)(High-V) [DX0001]
PIC18F2420(ISP)(Low-V) [DX0001]
PIC18F2420@QFN28 [DX4014]
PIC18F2420@QFN28(ISP)(High-V) [DX0001]
PIC18F2420@QFN28(ISP)(Low-V) [DX0001]
PIC18F2420@SOIC28 [DX1033]
PIC18F2420@SOIC28(ISP)(High-V) [DX0001]
PIC18F2420@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2420@SSOP28 [DX1026]
PIC18F2420@SSOP28(ISP)(High-V) [DX0001]
PIC18F2420@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2423 [DX0001]
PIC18F2423(ISP)(High-V) [DX0001]
PIC18F2423(ISP)(Low-V) [DX0001]
PIC18F2423@QFN28 [DX4014]
PIC18F2423@QFN28(ISP)(High-V) [DX0001]
PIC18F2423@QFN28(ISP)(Low-V) [DX0001]
PIC18F2423@SOIC28 [DX1033]
PIC18F2423@SOIC28(ISP)(High-V) [DX0001]
PIC18F2423@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2423@SSOP28 [DX1026]
PIC18F2423@SSOP28(ISP)(High-V) [DX0001]
PIC18F2423@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2431 [DX0001]
PIC18F2431(ISP) [DX0001]
PIC18F2431@SOIC28 [DX1033]
PIC18F2431@SOIC28(ISP) [DX0001]
PIC18F2439 [DX0001]
PIC18F2439(ISP) [DX0001]
PIC18F2439@SOIC28 [DX1033]
PIC18F2439@SOIC28(ISP) [DX0001]
PIC18F2450 [DX0001]
PIC18F2450(ISP)(Low-V) [DX0001]
PIC18F2450@QFN28 [DX4014]
PIC18F2450@QFN28(ISP)(Low-V) [DX0001]
PIC18F2450@SOIC28 [DX1033]
PIC18F2450@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2450@SSOP28 [DX1026]

PIC18F2450@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2455 [DX0001]
PIC18F2455(ISP)(High-V) [DX0001]
PIC18F2455(ISP)(Low-V) [DX0001]
PIC18F2455@SOIC28 [DX1033]
PIC18F2455@SOIC28(ISP)(High-V) [DX0001]
PIC18F2455@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2455@SSOP28 [DX1026]
PIC18F2455@SSOP28(ISP)(High-V) [DX0001]
PIC18F2455@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2458 [DX0001]
PIC18F2458(ISP)(High-V) [DX0001]
PIC18F2458(ISP)(Low-V) [DX0001]
PIC18F2458@SOIC28 [DX1033]
PIC18F2458@SOIC28(ISP)(High-V) [DX0001]
PIC18F2458@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2458@SSOP28
PIC18F2458@SSOP28(ISP)(High-V) [DX0001]
PIC18F2458@SSOP28(ISP)(Low-V) [DX0001]
PIC18F248 [DX0001]
PIC18F248(ISP) [DX0001]
PIC18F248@SOIC28 [DX1033]
PIC18F248@SOIC28(ISP) [DX0001]
PIC18F2480 [DX0001]
PIC18F2480(ISP)(High-V) [DX0001]
PIC18F2480(ISP)(Low-V) [DX0001]
PIC18F2480@QFN28 [DX4014]
PIC18F2480@QFN28(ISP)(High-V) [DX0001]
PIC18F2480@QFN28(ISP)(Low-V) [DX0001]
PIC18F2480@SOIC28 [DX1033]
PIC18F2480@SOIC28(ISP)(High-V) [DX0001]
PIC18F2480@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2480@SSOP28 [DX1026]
PIC18F2480@SSOP28(ISP)(High-V) [DX0001]
PIC18F2480@SSOP28(ISP)(Low-V) [DX0001]
PIC18F24J10 [DX0001]
PIC18F24J10(ISP) [DX0001]
PIC18F24J10@QFN28 [DX4014]
PIC18F24J10@QFN28(ISP) [DX0001]
PIC18F24J10@SOIC28 [DX1033]
PIC18F24J10@SOIC28(ISP) [DX0001]
PIC18F24J10@SSOP28 [DX1026]
PIC18F24J10@SSOP28(ISP) [DX0001]
PIC18F24J11 [DX0001]
PIC18F24J11(ISP) [DX0001]
PIC18F24J11@QFN28 [DX4014]
PIC18F24J11@QFN28(ISP) [DX0001]
PIC18F24J11@SOIC28 [DX1033]
PIC18F24J11@SOIC28(ISP) [DX0001]
PIC18F24J11@SSOP28 [DX1026]
PIC18F24J11@SSOP28(ISP) [DX0001]
PIC18F24J50 [DX0001]
PIC18F24J50(ISP) [DX0001]
PIC18F24J50@QFN28 [DX4014]
PIC18F24J50@QFN28(ISP) [DX0001]
PIC18F24J50@SOIC28 [DX1033]
PIC18F24J50@SOIC28(ISP) [DX0001]
PIC18F24J50@SSOP28 [DX1026]
PIC18F24J50@SSOP28(ISP) [DX0001]
PIC18F24K20 [DX0001]
PIC18F24K20(ISP)(High-V) [DX0001]
PIC18F24K20(ISP)(Low-V) [DX0001]
PIC18F24K20@QFN28 [DX4014]
PIC18F24K20@QFN28(ISP)(High-V) [DX0001]
PIC18F24K20@QFN28(ISP)(Low-V) [DX0001]
PIC18F24K20@SOIC28 [DX1033]
PIC18F24K20@SOIC28(ISP)(High-V) [DX0001]
PIC18F24K20@SOIC28(ISP)(Low-V) [DX0001]
PIC18F24K20@SSOP28 [DX1077]

PIC18F24K20@SSOP28(ISP)(High-V) [DX0001]
PIC18F24K20@SSOP28(ISP)(Low-V) [DX0001]
PIC18F24K20@UQFN28 [DX4036]
PIC18F24K22 [DX0001]
PIC18F24K22(ISP)(H-V) [DX0001]
PIC18F24K22@QFN28 [DX4014]
PIC18F24K22@QFN28(ISP)(H-V) [DX0001]
PIC18F24K22@SOIC28 [DX1033]
PIC18F24K22@SOIC28(ISP)(H-V) [DX0001]
PIC18F24K22@SSOP28 [DX1077]
PIC18F24K22@SSOP28(ISP)(H-V) [DX0001]
PIC18F24K22@UQFN28 [DX4036]
PIC18F24K50 [DX0001]
PIC18F24K50@ISP [DX0001]
PIC18F24K50@QFN28 [DX4014]
PIC18F24K50@SOIC28 [DX1033]
PIC18F24K50@SSOP28 [DX1077]
PIC18F2510 [DX0001]
PIC18F2510(ISP) [DX0001]
PIC18F2510@QFN28 [DX4014]
PIC18F2510@QFN28(ISP) [DX0001]
PIC18F2510@SOIC28 [DX1033]
PIC18F2510@SOIC28(ISP) [DX0001]
PIC18F2510@SSOP28 [DX1026]
PIC18F2510@SSOP28(ISP) [DX0001]
PIC18F2515 [DX0001]
PIC18F2515(ISP)(Low-V) [DX0001]
PIC18F2515@SOIC28 [DX1033]
PIC18F2515@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2515@SSOP28 [DX1026]
PIC18F2515@SSOP28(ISP)(Low-V) [DX0001]
PIC18F252 [DX0001]
PIC18F252(ISP) [DX0001]
PIC18F252@SOIC28 [DX1033]
PIC18F252@SOIC28(ISP) [DX0001]
PIC18F2520 [DX0001]
PIC18F2520(ISP)(High-V) [DX0001]
PIC18F2520(ISP)(Low-V) [DX0001]
PIC18F2520@QFN28 [DX4014]
PIC18F2520@QFN28(ISP)(High-V) [DX0001]
PIC18F2520@QFN28(ISP)(Low-V) [DX0001]
PIC18F2520@SOIC28 [DX1033]
PIC18F2520@SOIC28(ISP)(High-V) [DX0001]
PIC18F2520@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2520@SSOP28 [DX1026]
PIC18F2520@SSOP28(ISP)(High-V) [DX0001]
PIC18F2520@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2523(ISP)(High-V) [DX0001]
PIC18F2523(ISP)(Low-V) [DX0001]
PIC18F2523(REV4=0) [DX0001]
PIC18F2523(REV4=1) [DX0001]
PIC18F2523@QFN28(ISP)(High-V) [DX0001]
PIC18F2523@QFN28(ISP)(Low-V) [DX0001]
PIC18F2523@QFN28(REV4=0) [DX4014]
PIC18F2523@QFN28(REV4=1) [DX4014]
PIC18F2523@SOIC28(ISP)(High-V) [DX0001]
PIC18F2523@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2523@SOIC28(REV4=0) [DX1033]
PIC18F2523@SOIC28(REV4=1) [DX1033]
PIC18F2523@SSOP28(ISP)(High-V) [DX0001]
PIC18F2523@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2523@SSOP28(REV4=0) [DX1026]
PIC18F2523@SSOP28(REV4=1) [DX1026]
PIC18F2525 [DX0001]
PIC18F2525(ISP)(Low-V) [DX0001]

PIC18F2525@SOIC28 [DX1033]
PIC18F2525@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2525@SSOP28 [DX1026]
PIC18F2525@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2539 [DX0001]
PIC18F2539(ISP) [DX0001]
PIC18F2539@SOIC28 [DX1033]
PIC18F2539@SOIC28(ISP) [DX0001]
PIC18F2550 [DX0001]
PIC18F2550(ISP)(High-V) [DX0001]
PIC18F2550(ISP)(Low-V) [DX0001]
PIC18F2550@SOIC28 [DX1033]
PIC18F2550@SOIC28(ISP)(High-V) [DX0001]
PIC18F2550@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2550@SSOP28 [DX1026]
PIC18F2550@SSOP28(ISP)(High-V) [DX0001]
PIC18F2550@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2553 [DX0001]
PIC18F2553(ISP)(High-V) [DX0001]
PIC18F2553(ISP)(Low-V) [DX0001]
PIC18F2553@SOIC28 [DX1033]
PIC18F2553@SOIC28(ISP)(High-V) [DX0001]
PIC18F2553@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2553@SSOP28
PIC18F2553@SSOP28(ISP)(High-V) [DX0001]
PIC18F2553@SSOP28(ISP)(Low-V) [DX0001]
PIC18F258 [DX0001]
PIC18F258(ISP) [DX0001]
PIC18F258@SOIC28 [DX1033]
PIC18F258@SOIC28(ISP) [DX0001]
PIC18F2580 [DX0001]
PIC18F2580(ISP)(High-V) [DX0001]
PIC18F2580(ISP)(Low-V) [DX0001]
PIC18F2580@QFN28 [DX4014]
PIC18F2580@QFN28(ISP)(High-V) [DX0001]
PIC18F2580@QFN28(ISP)(Low-V) [DX0001]
PIC18F2580@SOIC28 [DX1033]
PIC18F2580@SOIC28(ISP)(High-V) [DX0001]
PIC18F2580@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2580@SSOP28 [DX1026]
PIC18F2580@SSOP28(ISP)(High-V) [DX0001]
PIC18F2580@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2585 [DX0001]
PIC18F2585(ISP)(High-V) [DX0001]
PIC18F2585(ISP)(Low-V) [DX0001]
PIC18F2585@SDIP28 [DX0032]
PIC18F2585@SDIP28(ISP)(High-V) [DX0001]
PIC18F2585@SDIP28(ISP)(Low-V) [DX0001]
PIC18F2585@SOIC28 [DX1033]
PIC18F2585@SOIC28(ISP)(High-V) [DX0001]
PIC18F2585@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2585@SSOP28 [DX1026]
PIC18F2585@SSOP28(ISP)(High-V) [DX0001]
PIC18F2585@SSOP28(ISP)(Low-V) [DX0001]
PIC18F25J10 [DX0001]
PIC18F25J10(ISP) [DX0001]
PIC18F25J10@QFN28 [DX4014]
PIC18F25J10@QFN28(ISP) [DX0001]
PIC18F25J10@SOIC28 [DX1033]
PIC18F25J10@SOIC28(ISP) [DX0001]
PIC18F25J10@SSOP28 [DX1026]
PIC18F25J10@SSOP28(ISP) [DX0001]
PIC18F25J11 [DX0001]
PIC18F25J11(ISP) [DX0001]
PIC18F25J11@QFN28 [DX4014]
PIC18F25J11@QFN28(ISP) [DX0001]

PIC18F25J11@SOIC28 [DX1033]
PIC18F25J11@SOIC28(ISP) [DX0001]
PIC18F25J11@SSOP28 [DX1026]
PIC18F25J11@SSOP28(ISP) [DX0001]
PIC18F25J50 [DX0001]
PIC18F25J50(ISP) [DX0001]
PIC18F25J50@QFN28 [DX4014]
PIC18F25J50@QFN28(ISP) [DX0001]
PIC18F25J50@SOIC28 [DX1033]
PIC18F25J50@SOIC28(ISP) [DX0001]
PIC18F25J50@SSOP28 [DX1026]
PIC18F25J50@SSOP28(ISP) [DX0001]
PIC18F25K20 [DX0001]
PIC18F25K20(ISP)(High-V) [DX0001]
PIC18F25K20(ISP)(Low-V) [DX0001]
PIC18F25K20@QFN28 [DX4014]
PIC18F25K20@QFN28(ISP)(High-V) [DX0001]
PIC18F25K20@QFN28(ISP)(Low-V) [DX0001]
PIC18F25K20@SOIC28 [DX1033]
PIC18F25K20@SOIC28(ISP)(High-V) [DX0001]
PIC18F25K20@SOIC28(ISP)(Low-V) [DX0001]
PIC18F25K20@SSOP28 [DX1077]
PIC18F25K20@SSOP28(ISP)(High-V) [DX0001]
PIC18F25K20@SSOP28(ISP)(Low-V) [DX0001]
PIC18F25K20@UQFN28 [DX4036]
PIC18F25K22 [DX0001]
PIC18F25K22(ISP)(H-V) [DX0001]
PIC18F25K22@QFN28 [DX4014]
PIC18F25K22@QFN28(ISP)(H-V) [DX0001]
PIC18F25K22@SOIC28 [DX1033]
PIC18F25K22@SOIC28(ISP)(H-V) [DX0001]
PIC18F25K22@SSOP28 [DX1077]
PIC18F25K22@SSOP28(ISP)(H-V) [DX0001]
PIC18F25K22@UQFN28 [DX4036]
PIC18F25K50 [DX0001]
PIC18F25K50@ISP [DX0001]
PIC18F25K50@QFN28 [DX4014]
PIC18F25K50@SOIC28 [DX1033]
PIC18F25K50@SSOP28 [DX1077]
PIC18F25K80 [DX0001]
PIC18F25K80(ISP) [DX0001]
PIC18F25K80@QFN28 [DX4014]
PIC18F25K80@QFN28(ISP) [DX0001]
PIC18F25K80@SOIC28 [DX1033]
PIC18F25K80@SOIC28(ISP) [DX0001]
PIC18F25K80@SSOP28 [DX1026]
PIC18F25K80@SSOP28(ISP) [DX0001]
PIC18F2610 [DX0001]
PIC18F2610(ISP)(Low-V) [DX0001]
PIC18F2610@SOIC28 [DX1033]
PIC18F2610@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2610@SSOP28 [DX1026]
PIC18F2610@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2620 [DX0001]
PIC18F2620(ISP)(Low-V) [DX0001]
PIC18F2620@SOIC28 [DX1033]
PIC18F2620@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2620@SSOP28 [DX1026]
PIC18F2620@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2680 [DX0001]
PIC18F2680(ISP)(High-V) [DX0001]
PIC18F2680(ISP)(Low-V) [DX0001]
PIC18F2680@SDIP28 [DX0032]
PIC18F2680@SDIP28(ISP)(High-V) [DX0001]
PIC18F2680@SDIP28(ISP)(Low-V) [DX0001]
PIC18F2680@SOIC28 [DX1033]
PIC18F2680@SOIC28(ISP)(High-V) [DX0001]
PIC18F2680@SOIC28(ISP)(Low-V) [DX0001]

PIC18F2680@SSOP28 [DX1026]
PIC18F2680@SSOP28(ISP)(High-V) [DX0001]
PIC18F2680@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2682 [DX0001]
PIC18F2682(ISP)(High-V) [DX0001]
PIC18F2682(ISP)(Low-V) [DX0001]
PIC18F2682@QFN28 [DX4014]
PIC18F2682@QFN28(ISP)(High-V) [DX0001]
PIC18F2682@QFN28(ISP)(Low-V) [DX0001]
PIC18F2682@SOIC28 [DX1033]
PIC18F2682@SOIC28(ISP)(High-V) [DX0001]
PIC18F2682@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2682@SSOP28 [DX1026]
PIC18F2682@SSOP28(ISP)(High-V) [DX0001]
PIC18F2682@SSOP28(ISP)(Low-V) [DX0001]
PIC18F2685 [DX0001]
PIC18F2685(ISP)(High-V) [DX0001]
PIC18F2685(ISP)(Low-V) [DX0001]
PIC18F2685@QFN28 [DX4014]
PIC18F2685@QFN28(ISP)(High-V) [DX0001]
PIC18F2685@QFN28(ISP)(Low-V) [DX0001]
PIC18F2685@SOIC28 [DX1033]
PIC18F2685@SOIC28(ISP)(High-V) [DX0001]
PIC18F2685@SOIC28(ISP)(Low-V) [DX0001]
PIC18F2685@SSOP28 [DX1026]
PIC18F2685@SSOP28(ISP)(High-V) [DX0001]
PIC18F2685@SSOP28(ISP)(Low-V) [DX0001]
PIC18F26J11 [DX0001]
PIC18F26J11(ISP) [DX0001]
PIC18F26J11@QFN28 [DX4014]
PIC18F26J11@QFN28(ISP) [DX0001]
PIC18F26J11@SOIC28 [DX1033]
PIC18F26J11@SOIC28(ISP) [DX0001]
PIC18F26J11@SSOP28 [DX1026]
PIC18F26J11@SSOP28(ISP) [DX0001]
PIC18F26J13 [DX0001]
PIC18F26J13(ISP) [DX0001]
PIC18F26J13@QFN28 [DX4014]
PIC18F26J13@QFN28(ISP) [DX0001]
PIC18F26J13@SOIC28 [DX1033]
PIC18F26J13@SOIC28(ISP) [DX0001]
PIC18F26J13@SSOP28 [DX1026]
PIC18F26J13@SSOP28(ISP) [DX0001]
PIC18F26J50 [DX0001]
PIC18F26J50(ISP) [DX0001]
PIC18F26J50@QFN28 [DX4014]
PIC18F26J50@QFN28(ISP) [DX0001]
PIC18F26J50@SOIC28 [DX1033]
PIC18F26J50@SOIC28(ISP) [DX0001]
PIC18F26J50@SSOP28 [DX1026]
PIC18F26J50@SSOP28(ISP) [DX0001]
PIC18F26J53 [DX0001]
PIC18F26J53(ISP) [DX0001]
PIC18F26J53@QFN28 [DX4014]
PIC18F26J53@QFN28(ISP) [DX0001]
PIC18F26J53@SOIC28 [DX1033]
PIC18F26J53@SOIC28(ISP) [DX0001]
PIC18F26J53@SSOP28 [DX1026]
PIC18F26J53@SSOP28(ISP) [DX0001]
PIC18F26K20 [DX0001]
PIC18F26K20(ISP)(High-V) [DX0001]
PIC18F26K20(ISP)(Low-V) [DX0001]
PIC18F26K20@QFN28 [DX4014]
PIC18F26K20@QFN28(ISP)(High-V) [DX0001]
PIC18F26K20@QFN28(ISP)(Low-V) [DX0001]
PIC18F26K20@SOIC28 [DX1033]
PIC18F26K20@SOIC28(ISP)(High-V) [DX0001]
PIC18F26K20@SOIC28(ISP)(Low-V) [DX0001]
PIC18F26K20@SSOP28 [DX1077]

PIC18F26K20@SSOP28(ISP)(High-V) [DX0001]
PIC18F26K20@SSOP28(ISP)(Low-V) [DX0001]
PIC18F26K20@UQFN28 [DX4036]
PIC18F26K22 [DX0001]
PIC18F26K22(ISP)(H-V) [DX0001]
PIC18F26K22@QFN28 [DX4014]
PIC18F26K22@QFN28(ISP)(H-V) [DX0001]
PIC18F26K22@SOIC28 [DX1033]
PIC18F26K22@SOIC28(ISP)(H-V) [DX0001]
PIC18F26K22@SSOP28 [DX1077]
PIC18F26K22@SSOP28(ISP)(H-V) [DX0001]
PIC18F26K22@UQFN28 [DX4036]
PIC18F26K50 [DX0001]
PIC18F26K50@ISP [DX0001]
PIC18F26K50@QFN28 [DX4014]
PIC18F26K50@SOIC28 [DX1033]
PIC18F26K50@SSOP28 [DX1077]
PIC18F26K80 [DX0001]
PIC18F26K80(ISP) [DX0001]
PIC18F26K80@QFN28 [DX4014]
PIC18F26K80@QFN28(ISP) [DX0001]
PIC18F26K80@SOIC28 [DX1033]
PIC18F26K80@SOIC28(ISP) [DX0001]
PIC18F26K80@SSOP28 [DX1026]
PIC18F26K80@SSOP28(ISP) [DX0001]
PIC18F27J13 [DX0001]
PIC18F27J13(ISP) [DX0001]
PIC18F27J13@QFN28 [DX4014]
PIC18F27J13@QFN28(ISP) [DX0001]
PIC18F27J13@SOIC28 [DX1033]
PIC18F27J13@SOIC28(ISP) [DX0001]
PIC18F27J13@SSOP28 [DX1026]
PIC18F27J13@SSOP28(ISP) [DX0001]
PIC18F27J53 [DX0001]
PIC18F27J53(ISP) [DX0001]
PIC18F27J53@QFN28 [DX4014]
PIC18F27J53@QFN28(ISP) [DX0001]
PIC18F27J53@SOIC28 [DX1033]
PIC18F27J53@SOIC28(ISP) [DX0001]
PIC18F27J53@SSOP28 [DX1026]
PIC18F27J53@SSOP28(ISP) [DX0001]
PIC18F4220 [DX0001]
PIC18F4220(ISP) [DX0001]
PIC18F4220@QFN44 [DX4018]
PIC18F4220@QFN44(ISP) [DX0001]
PIC18F4220@QFN44(ML) [DX4019]
PIC18F4220@QFN44(ML)(ISP) [DX0001]
PIC18F4220@TQFP44 [DX3003]
PIC18F4220@TQFP44(ISP) [DX0001]
PIC18F4221 [DX0001]
PIC18F4221(ISP)(Low-V) [DX0001]
PIC18F4221@QFN44 [DX4018]
PIC18F4221@QFN44(ISP)(Low-V) [DX0001]
PIC18F4221@QFN44(ML) [DX4019]
PIC18F4221@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4221@TQFP44 [DX3003]
PIC18F4221@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4320 [DX0001]
PIC18F4320(ISP) [DX0001]
PIC18F4320@QFN44 [DX4018]
PIC18F4320@QFN44(ISP) [DX0001]
PIC18F4320@QFN44(ML) [DX4019]
PIC18F4320@QFN44(ML)(ISP) [DX0001]
PIC18F4320@TQFP44 [DX3003]
PIC18F4320@TQFP44(ISP) [DX0001]
PIC18F4321 [DX0001]
PIC18F4321(ISP)(Low-V) [DX0001]
PIC18F4321@QFN44 [DX4018]
PIC18F4321@QFN44(ISP)(Low-V) [DX0001]
PIC18F4321@QFN44(ML) [DX4019]
PIC18F4321@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4321@TQFP44 [DX3003]
PIC18F4321@TQFP44(ISP)(Low-V) [DX0001]

PIC18F4331 [DX0001]
PIC18F4331(ISP) [DX0001]
PIC18F4331@TQFP44 [DX3003]
PIC18F4331@TQFP44(ISP) [DX0001]
PIC18F43K20 [DX0001]
PIC18F43K20(ISP)(High-V) [DX0001]
PIC18F43K20(ISP)(Low-V) [DX0001]
PIC18F43K20@QFN44 [DX4018]
PIC18F43K20@QFN44(ISP)(High-V) [DX0001]
PIC18F43K20@QFN44(ISP)(Low-V) [DX0001]
PIC18F43K20@QFN44(ML) [DX4019]
PIC18F43K20@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F43K20@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18F43K20@TQFP44 [DX3003]
PIC18F43K20@TQFP44(ISP)(High-V) [DX0001]
PIC18F43K20@TQFP44(ISP)(Low-V) [DX0001]
PIC18F43K20@UQFN40 [DX4039]
PIC18F43K22 [DX0001]
PIC18F43K22(ISP)(H-V) [DX0001]
PIC18F43K22@QFN44 [DX4018]
PIC18F43K22@QFN44(ISP)(H-V) [DX0001]
PIC18F43K22@QFN44(ML) [DX4019]
PIC18F43K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F43K22@TQFP44 [DX3003]
PIC18F43K22@TQFP44(ISP)(H-V) [DX0001]
PIC18F43K22@UQFN40 [DX4039]
PIC18F4410 [DX0001]
PIC18F4410(ISP)(Low-V) [DX0001]
PIC18F4410@QFN44 [DX4018]
PIC18F4410@QFN44(ISP)(Low-V) [DX0001]
PIC18F4410@QFN44(ML) [DX4019]
PIC18F4410@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4410@TQFP44 [DX3003]
PIC18F4410@TQFP44(ISP)(Low-V) [DX0001]
PIC18F442 [DX0001]
PIC18F442(ISP) [DX0001]
PIC18F442@PLCC44 [DX2044]
PIC18F442@PLCC44(ISP) [DX0001]
PIC18F442@QFN44 [DX4019]
PIC18F442@TQFP44 [DX3003]
PIC18F442@TQFP44(ISP) [DX0001]
PIC18F4420 [DX0001]
PIC18F4420(ISP)(Low-V) [DX0001]
PIC18F4420@QFN44 [DX4018]
PIC18F4420@QFN44(ISP)(Low-V) [DX0001]
PIC18F4420@QFN44(ML) [DX4019]
PIC18F4420@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4420@TQFP44 [DX3003]
PIC18F4420@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4423 [DX0001]
PIC18F4423(ISP)(High-V) [DX0001]
PIC18F4423(ISP)(Low-V) [DX0001]
PIC18F4423@QFN44 [DX4018]
PIC18F4423@QFN44(ISP)(High-V) [DX0001]
PIC18F4423@QFN44(ISP)(Low-V) [DX0001]
PIC18F4423@QFN44(ML) [DX4019]
PIC18F4423@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4423@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4423@TQFP44 [DX3003]
PIC18F4423@TQFP44(ISP)(High-V) [DX0001]
PIC18F4423@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4431 [DX0001]
PIC18F4431(ISP) [DX0001]

PIC18F4431@TQFP44 [DX3003]
PIC18F4431@TQFP44(ISP) [DX0001]
PIC18F4439 [DX0001]
PIC18F4439(ISP) [DX0001]
PIC18F4439@TQFP44 [DX3003]
PIC18F4439@TQFP44(ISP) [DX0001]
PIC18F4450 [DX0001]
PIC18F4450(ISP)(Low-V) [DX0001]
PIC18F4450@QFN44 [DX4018]
PIC18F4450@QFN44(ISP)(Low-V) [DX0001]
PIC18F4450@QFN44(ML) [DX4019]
PIC18F4450@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4450@TQFP44 [DX3003]
PIC18F4450@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4455 [DX0001]
PIC18F4455(ISP)(High-V) [DX0001]
PIC18F4455(ISP)(Low-V) [DX0001]
PIC18F4455@QFN44 [DX4018]
PIC18F4455@QFN44(ISP)(High-V) [DX0001]
PIC18F4455@QFN44(ISP)(Low-V) [DX0001]
PIC18F4455@QFN44(ML) [DX4019]
PIC18F4455@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4455@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4455@TQFP44 [DX3003]
PIC18F4455@TQFP44(ISP)(High-V) [DX0001]
PIC18F4455@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4458 [DX0001]
PIC18F4458(ISP)(High-V) [DX0001]
PIC18F4458(ISP)(Low-V) [DX0001]
PIC18F4458@QFN44 [DX4018]
PIC18F4458@QFN44(ISP)(High-V) [DX0001]
PIC18F4458@QFN44(ISP)(Low-V) [DX0001]
PIC18F4458@TQFP44 [DX3003]
PIC18F4458@TQFP44(ISP)(High-V) [DX0001]
PIC18F4458@TQFP44(ISP)(Low-V) [DX0001]
PIC18F448 [DX0001]
PIC18F448(ISP) [DX0001]
PIC18F448@PLCC44 [DX2044]
PIC18F448@PLCC44(ISP) [DX0001]
PIC18F448@QFN44 [DX4019]
PIC18F448@TQFP44 [DX3003]
PIC18F448@TQFP44(ISP) [DX0001]
PIC18F4480 [DX0001]
PIC18F4480(ISP)(High-V) [DX0001]
PIC18F4480(ISP)(Low-V) [DX0001]
PIC18F4480@QFN44 [DX4018]
PIC18F4480@QFN44(ISP)(High-V) [DX0001]
PIC18F4480@QFN44(ISP)(Low-V) [DX0001]
PIC18F4480@QFN44(ML) [DX4019]
PIC18F4480@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4480@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4480@TQFP44 [DX3003]
PIC18F4480@TQFP44(ISP)(High-V) [DX0001]
PIC18F4480@TQFP44(ISP)(Low-V) [DX0001]
PIC18F44J10 [DX0001]
PIC18F44J10(ISP) [DX0001]
PIC18F44J10@QFN44 [DX4018]
PIC18F44J10@QFN44(ISP) [DX0001]
PIC18F44J10@QFN44(ML) [DX4019]
PIC18F44J10@QFN44(ML)(ISP) [DX0001]
PIC18F44J10@TQFP44 [DX3003]
PIC18F44J10@TQFP44(ISP) [DX0001]
PIC18F44J11 [DX0001]
PIC18F44J11(ISP) [DX0001]
PIC18F44J11@QFN44 [DX4018]
PIC18F44J11@QFN44(ISP) [DX0001]

PIC18F44J11@QFN44(ML) [DX4019]
PIC18F44J11@QFN44(ML)(ISP) [DX0001]
PIC18F44J11@TQFP44 [DX3003]
PIC18F44J11@TQFP44(ISP) [DX0001]
PIC18F44J50 [DX0001]
PIC18F44J50(ISP) [DX0001]
PIC18F44J50@QFN44 [DX4018]
PIC18F44J50@QFN44(ISP) [DX0001]
PIC18F44J50@QFN44(ML) [DX4019]
PIC18F44J50@QFN44(ML)(ISP) [DX0001]
PIC18F44J50@TQFP44 [DX3003]
PIC18F44J50@TQFP44(ISP) [DX0001]
PIC18F44K20 [DX0001]
PIC18F44K20(ISP)(High-V) [DX0001]
PIC18F44K20(ISP)(Low-V) [DX0001]
PIC18F44K20@QFN44 [DX4018]
PIC18F44K20@QFN44(ISP)(High-V) [DX0001]
PIC18F44K20@QFN44(ISP)(Low-V) [DX0001]
PIC18F44K20@QFN44(ML) [DX4019]
PIC18F44K20@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F44K20@QFN44(ML)(ISP)(L-V) [DX4018]
PIC18F44K20@TQFP44 [DX3003]
PIC18F44K20@TQFP44(ISP)(High-V) [DX0001]
PIC18F44K20@TQFP44(ISP)(Low-V) [DX0001]
PIC18F44K20@UQFN40 [DX4039]
PIC18F44K22 [DX0001]
PIC18F44K22(ISP)(H-V) [DX0001]
PIC18F44K22@QFN44 [DX4018]
PIC18F44K22@QFN44(ISP)(H-V) [DX0001]
PIC18F44K22@QFN44(ML) [DX4019]
PIC18F44K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F44K22@TQFP44 [DX3003]
PIC18F44K22@TQFP44(ISP)(H-V) [DX0001]
PIC18F44K22@UQFN40 [DX4039]
PIC18F4510 [DX0001]
PIC18F4510(ISP) [DX0001]
PIC18F4510@QFN44 [DX4018]
PIC18F4510@QFN44(ISP) [DX0001]
PIC18F4510@QFN44(ML) [DX4019]
PIC18F4510@QFN44(ML)(ISP) [DX0001]
PIC18F4510@TQFP44 [DX3003]
PIC18F4510@TQFP44(ISP) [DX0001]
PIC18F4515 [DX0001]
PIC18F4515(ISP)(Low-V) [DX0001]
PIC18F4515@QFN44 [DX4018]
PIC18F4515@QFN44(ISP)(Low-V) [DX0001]
PIC18F4515@QFN44(ML) [DX4019]
PIC18F4515@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4515@TQFP44 [DX3003]
PIC18F4515@TQFP44(ISP)(Low-V) [DX0001]
PIC18F452 [DX0001]
PIC18F452(ISP) [DX0001]
PIC18F452@PLCC44 [DX2044]
PIC18F452@PLCC44(ISP) [DX0001]
PIC18F452@QFN44 [DX4019]
PIC18F452@TQFP44 [DX3003]
PIC18F452@TQFP44(ISP) [DX0001]
PIC18F4520 [DX0001]
PIC18F4520(ISP) [DX0001]
PIC18F4520@QFN44 [DX4018]
PIC18F4520@QFN44(ISP) [DX0001]
PIC18F4520@QFN44(ML) [DX4019]
PIC18F4520@QFN44(ML)(ISP) [DX0001]
PIC18F4520@TQFP44 [DX3003]
PIC18F4520@TQFP44(ISP) [DX0001]
PIC18F4523 [DX0001]
PIC18F4523(ISP)(High-V) [DX0001]
PIC18F4523(ISP)(Low-V) [DX0001]
PIC18F4523@QFN44 [DX4018]

PIC18F4523@QFN44(ISP)(High-V) [DX0001]
PIC18F4523@QFN44(ISP)(Low-V) [DX0001]
PIC18F4523@QFN44(ML) [DX4019]
PIC18F4523@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4523@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4523@TQFP44 [DX3003]
PIC18F4523@TQFP44(ISP)(High-V) [DX0001]
PIC18F4523@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4525 [DX0001] PIC18F4525(ISP)(Low-V) [DX0001]
PIC18F4525@QFN44 [DX4018]
PIC18F4525@QFN44(ISP)(Low-V) [DX0001]
PIC18F4525@QFN44(ML) [DX4019]
PIC18F4525@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4525@TQFP44 [DX3003]
PIC18F4525@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4539 [DX0001] PIC18F4539(ISP) [DX0001]
PIC18F4539@TQFP44 [DX3003] PIC18F4539@TQFP44(ISP) [DX0001]
PIC18F4550 [DX0001] PIC18F4550(ISP)(High-V) [DX0001]
PIC18F4550(ISP)(Low-V) [DX0001] PIC18F4550@QFN44 [DX4018]
PIC18F4550@QFN44(ISP)(High-V) [DX0001]
PIC18F4550@QFN44(ISP)(Low-V) [DX0001]
PIC18F4550@QFN44(ML) [DX4019]
PIC18F4550@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4550@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4550@TQFP44 [DX3003]
PIC18F4550@TQFP44(ISP)(High-V) [DX0001]
PIC18F4550@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4553 [DX0001] PIC18F4553(ISP)(High-V) [DX0001]
PIC18F4553(ISP)(Low-V) [DX0001] PIC18F4553@QFN44 [DX4018]
PIC18F4553@QFN44(ISP)(High-V) [DX0001]
PIC18F4553@QFN44(ISP)(Low-V) [DX0001]
PIC18F4553@TQFP44 [DX3003]
PIC18F4553@TQFP44(ISP)(High-V) [DX0001]
PIC18F4553@TQFP44(ISP)(Low-V) [DX0001]
PIC18F458 [DX0001] PIC18F458(ISP) [DX0001]
PIC18F458@PLCC44 [DX2044] PIC18F458@PLCC44(ISP) [DX0001]
PIC18F458@QFN44 [DX4019] PIC18F458@TQFP44 [DX3003]
PIC18F458@TQFP44(ISP) [DX0001] PIC18F4580 [DX0001]
PIC18F4580(ISP)(High-V) [DX0001] PIC18F4580(ISP)(Low-V) [DX0001]
PIC18F4580@QFN44 [DX4018]
PIC18F4580@QFN44(ISP)(High-V) [DX0001]
PIC18F4580@QFN44(ISP)(Low-V) [DX0001]
PIC18F4580@QFN44(ML) [DX4019]
PIC18F4580@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4580@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4580@TQFP44 [DX3003]
PIC18F4580@TQFP44(ISP)(High-V) [DX0001]
PIC18F4580@TQFP44(ISP)(Low-V) [DX0001]

PIC18F4585 [DX0001]
PIC18F4585(ISP)(High-V) [DX0001]
PIC18F4585(ISP)(Low-V) [DX0001]
PIC18F4585@QFN44 [DX4018]
PIC18F4585@QFN44(ISP)(High-V) [DX0001]
PIC18F4585@QFN44(ISP)(Low-V) [DX0001]
PIC18F4585@QFN44(ML) [DX4019]
PIC18F4585@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4585@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4585@TQFP44 [DX3003]
PIC18F4585@TQFP44(ISP)(High-V) [DX0001]
PIC18F4585@TQFP44(ISP)(Low-V) [DX0001]
PIC18F45J10 [DX0001]
PIC18F45J10(ISP) [DX0001]
PIC18F45J10@QFN44 [DX4018]
PIC18F45J10@QFN44(ISP) [DX0001]
PIC18F45J10@QFN44(ML) [DX4019]
PIC18F45J10@QFN44(ML)(ISP) [DX0001]
PIC18F45J10@TQFP44 [DX3003]
PIC18F45J10@TQFP44(ISP) [DX0001]
PIC18F45J11 [DX0001]
PIC18F45J11(ISP) [DX0001]
PIC18F45J11@QFN44 [DX4018]
PIC18F45J11@QFN44(ISP) [DX0001]
PIC18F45J11@QFN44(ML) [DX4019]
PIC18F45J11@QFN44(ML)(ISP) [DX0001]
PIC18F45J11@TQFP44 [DX3003]
PIC18F45J11@TQFP44(ISP) [DX0001]
PIC18F45J50 [DX0001]
PIC18F45J50(ISP) [DX0001]
PIC18F45J50@QFN44 [DX4018]
PIC18F45J50@QFN44(ISP) [DX0001]
PIC18F45J50@QFN44(ML) [DX4019]
PIC18F45J50@QFN44(ML)(ISP) [DX0001]
PIC18F45J50@TQFP44 [DX3003]
PIC18F45J50@TQFP44(ISP) [DX0001]
PIC18F45K20 [DX0001]
PIC18F45K20(ISP)(High-V) [DX0001]
PIC18F45K20(ISP)(Low-V) [DX0001]
PIC18F45K20@QFN44 [DX4018]
PIC18F45K20@QFN44(ISP)(High-V) [DX0001]
PIC18F45K20@QFN44(ISP)(Low-V) [DX0001]
PIC18F45K20@QFN44(ML) [DX4019]
PIC18F45K20@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F45K20@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18F45K20@TQFP44 [DX3003]
PIC18F45K20@TQFP44(ISP)(High-V) [DX0001]
PIC18F45K20@TQFP44(ISP)(Low-V) [DX0001]
PIC18F45K20@UQFN40 [DX4039]
PIC18F45K22 [DX0001]
PIC18F45K22(ISP)(H-V) [DX0001]
PIC18F45K22@QFN44 [DX4018]
PIC18F45K22@QFN44(ISP)(H-V) [DX0001]
PIC18F45K22@QFN44(ML) [DX4019]
PIC18F45K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F45K22@TQFP44 [DX3003]
PIC18F45K22@TQFP44(ISP)(H-V) [DX0001]
PIC18F45K22@UQFN40 [DX4039]
PIC18F45K50 [DX0001]
PIC18F45K50@ISP [DX0001]
PIC18F45K50@QFN44 [DX4019]
PIC18F45K50@TQFP44 [DX3003]
PIC18F45K50@UQFN40 [DX4039]
PIC18F45K80 [DX0001]
PIC18F45K80(ISP) [DX0001]
PIC18F45K80@QFN44 [DX4019]
PIC18F45K80@QFN44(ISP) [DX0001]

PIC18F45K80@TQFP44 [DX3003]
PIC18F45K80@TQFP44(ISP) [DX0001]
PIC18F4610 [DX0001]
PIC18F4610(ISP)(Low-V) [DX0001]
PIC18F4610@QFN44 [DX4018]
PIC18F4610@QFN44(ISP)(Low-V) [DX0001]
PIC18F4610@QFN44(ML) [DX4019]
PIC18F4610@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4610@TQFP44 [DX3003]
PIC18F4610@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4620 [DX0001]
PIC18F4620(ISP)(Low-V) [DX0001]
PIC18F4620@QFN44 [DX4018]
PIC18F4620@QFN44(ISP)(Low-V) [DX0001]
PIC18F4620@QFN44(ML) [DX4019]
PIC18F4620@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4620@TQFP44 [DX3003]
PIC18F4620@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4680 [DX0001]
PIC18F4680(ISP)(High-V) [DX0001]
PIC18F4680(ISP)(Low-V) [DX0001]
PIC18F4680@QFN44 [DX4018]
PIC18F4680@QFN44(ISP)(High-V) [DX0001]
PIC18F4680@QFN44(ISP)(Low-V) [DX0001]
PIC18F4680@QFN44(ML) [DX4019]
PIC18F4680@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4680@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4680@TQFP44 [DX3003]
PIC18F4680@TQFP44(ISP)(High-V) [DX0001]
PIC18F4680@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4682 [DX0001]
PIC18F4682(ISP)(High-V) [DX0001]
PIC18F4682(ISP)(Low-V) [DX0001]
PIC18F4682@QFN44 [DX4018]
PIC18F4682@QFN44(ISP)(High-V) [DX0001]
PIC18F4682@QFN44(ISP)(Low-V) [DX0001]
PIC18F4682@QFN44(ML) [DX4019]
PIC18F4682@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4682@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4682@TQFP44 [DX3003]
PIC18F4682@TQFP44(ISP)(High-V) [DX0001]
PIC18F4682@TQFP44(ISP)(Low-V) [DX0001]
PIC18F4685 [DX0001]
PIC18F4685(ISP)(High-V) [DX0001]
PIC18F4685(ISP)(Low-V) [DX0001]
PIC18F4685@QFN44 [DX4018]
PIC18F4685@QFN44(ISP)(High-V) [DX0001]
PIC18F4685@QFN44(ISP)(Low-V) [DX0001]
PIC18F4685@QFN44(ML) [DX4019]
PIC18F4685@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F4685@QFN44(ML)(ISP)(Low-V) [DX0001]
PIC18F4685@TQFP44 [DX3003]
PIC18F4685@TQFP44(ISP)(High-V) [DX0001]
PIC18F4685@TQFP44(ISP)(Low-V) [DX0001]
PIC18F46J11 [DX0001]
PIC18F46J11(ISP) [DX0001]
PIC18F46J11@QFN44 [DX4018]
PIC18F46J11@QFN44(ISP) [DX0001]
PIC18F46J11@QFN44(ML) [DX4019]

PIC18F46J11@QFN44(ML)(ISP) [DX0001]
PIC18F46J11@TQFP44 [DX3003]
PIC18F46J11@TQFP44(ISP) [DX0001]
PIC18F46J13 [DX0001]
PIC18F46J13(ISP) [DX0001]
PIC18F46J13@QFN44 [DX4018]
PIC18F46J13@QFN44(ML) [DX4019]
PIC18F46J13@TQFP44 [DX3003]
PIC18F46J13QFN44(ISP) [DX0001]
PIC18F46J13QFN44(ML)(ISP) [DX0001]
PIC18F46J13TQFP44(ISP) [DX0001]
PIC18F46J50 [DX0001]
PIC18F46J50(ISP) [DX0001]
PIC18F46J50@QFN44 [DX4018]
PIC18F46J50@QFN44(ISP) [DX0001]
PIC18F46J50@QFN44(ML) [DX4019]
PIC18F46J50@QFN44(ML)(ISP) [DX0001]
PIC18F46J50@TQFP44 [DX3003]
PIC18F46J50@TQFP44(ISP) [DX0001]
PIC18F46J53 [DX0001]
PIC18F46J53(ISP) [DX0001]
PIC18F46J53@QFN44 [DX4018]
PIC18F46J53@QFN44(ML) [DX4019]
PIC18F46J53@TQFP44 [DX3003]
PIC18F46J53QFN44(ISP) [DX0001]
PIC18F46J53QFN44(ML)(ISP) [DX0001]
PIC18F46J53TQFP44(ISP) [DX0001]
PIC18F46K20 [DX0001]
PIC18F46K20(ISP)(High-V) [DX0001]
PIC18F46K20(ISP)(Low-V) [DX0001]
PIC18F46K20@QFN44 [DX4018]
PIC18F46K20@QFN44(ISP)(High-V) [DX0001]
PIC18F46K20@QFN44(ISP)(Low-V) [DX0001]
PIC18F46K20@QFN44(ML) [DX4019]
PIC18F46K20@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F46K20@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18F46K20@TQFP44 [DX3003]
PIC18F46K20@TQFP44(ISP)(High-V) [DX0001]
PIC18F46K20@TQFP44(ISP)(Low-V) [DX0001]
PIC18F46K20@UQFN40 [DX4039]
PIC18F46K22 [DX0001]
PIC18F46K22(ISP)(H-V) [DX0001]
PIC18F46K22@QFN44 [DX4018]
PIC18F46K22@QFN44(ISP)(H-V) [DX0001]
PIC18F46K22@QFN44(ML) [DX4019]
PIC18F46K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18F46K22@TQFP44 [DX3003]
PIC18F46K22@TQFP44(ISP)(H-V) [DX0001]
PIC18F46K22@UQFN40 [DX4039]
PIC18F46K50 [DX0001]
PIC18F46K50@ISP [DX0001]
PIC18F46K50@QFN44 [DX4019]
PIC18F46K50@TQFP44 [DX3003]
PIC18F46K50@UQFN40 [DX4039]
PIC18F46K80 [DX0001]
PIC18F46K80(ISP) [DX0001]
PIC18F46K80@QFN44 [DX4019]
PIC18F46K80@QFN44(ISP) [DX0001]
PIC18F46K80@TQFP44 [DX3003]
PIC18F46K80@TQFP44(ISP) [DX0001]
PIC18F47J13 [DX0001]
PIC18F47J13(ISP) [DX0001]
PIC18F47J13@QFN44 [DX4018]
PIC18F47J13@QFN44(ML) [DX4019]
PIC18F47J13@TQFP44 [DX3003]
PIC18F47J13QFN44(ISP) [DX0001]
PIC18F47J13QFN44(ML)(ISP) [DX0001]
PIC18F47J13TQFP44(ISP) [DX0001]
PIC18F47J53 [DX0001]
PIC18F47J53(ISP) [DX0001]
PIC18F47J53@QFN44 [DX4018]
PIC18F47J53@QFN44(ML) [DX4019]
PIC18F47J53@TQFP44 [DX3003]
PIC18F47J53QFN44(ISP) [DX0001]
PIC18F47J53QFN44(ML)(ISP) [DX0001]

PIC18F47J53TQFP44(ISP) [DX0001]
PIC18F6310@TQFP64 [DX3011]
PIC18F6310@TQFP64(ISP) [DX0001]
PIC18F6390@TQFP64 [DX3011]
PIC18F6390@TQFP64(ISP) [DX0001]
PIC18F6393@TQFP64 [DX3011]
PIC18F6393@TQFP64(ISP) [DX0001]
PIC18F63J11@TQFP64 [DX3011]
PIC18F63J11@TQFP64(ISP) [DX0001]
PIC18F63J90@TQFP64 [DX3011]
PIC18F63J90@TQFP64(ISP) [DX0001]
PIC18F6410@TQFP64 [DX3011]
PIC18F6410@TQFP64(ISP) [DX0001]
PIC18F6490@TQFP64 [DX3011]
PIC18F6490@TQFP64(ISP) [DX0001]
PIC18F6493@TQFP64 [DX3011]
PIC18F6493@TQFP64(ISP) [DX0001]
PIC18F64J11@TQFP64 [DX3011]
PIC18F64J11@TQFP64(ISP) [DX0001]
PIC18F64J90@TQFP64 [DX3011]
PIC18F64J90@TQFP64(ISP) [DX0001]
PIC18F6520@TQFP64 [DX3011]
PIC18F6520@TQFP64(ISP) [DX0001]
PIC18F6525@TQFP64 [DX3011]
PIC18F6525@TQFP64(ISP) [DX0001]
PIC18F6527@TQFP64 [DX3011]
PIC18F6527@TQFP64(ISP)(High-V) [DX0001]
PIC18F6527@TQFP64(ISP)(Low-V) [DX0001]
PIC18F6585@PLCC68 [DX2068]
PIC18F6585@PLCC68(ISP) [DX0001]
PIC18F6585@TQFP64 [DX3011]
PIC18F6585@TQFP64(ISP) [DX0001]
PIC18F65J10@TQFP64 [DX3011]
PIC18F65J10@TQFP64(ISP) [DX0001]
PIC18F65J10@TQFP64(ISP)(Enable) [DX0001]
PIC18F65J11@TQFP64 [DX3011]
PIC18F65J11@TQFP64(ISP) [DX0001]
PIC18F65J15@TQFP64 [DX3011]
PIC18F65J15@TQFP64(ISP) [DX0001]
PIC18F65J15@TQFP64(ISP)(Enable) [DX0001]
PIC18F65J50@TQFP64 [DX3011]
PIC18F65J50@TQFP64(ISP) [DX0001]
PIC18F65J90@TQFP64 [DX3011]
PIC18F65J90@TQFP64(ISP) [DX0001]
PIC18F65K22(HVISP)(Disable) [DX0001]
PIC18F65K22(HVISP)(Enable) [DX0001]
PIC18F65K22(LVISP)(Disable) [DX0001]
PIC18F65K22(LVISP)(Enable) [DX0001]
PIC18F65K22@TQFP64(HV) [DX3011]
PIC18F65K22@TQFP64(LV) [DX3011]
PIC18F65K80@QFN64 [DX4023]
PIC18F65K80@QFN64(ISP) [DX0001]
PIC18F65K80@TQFP64 [DX3011]
PIC18F65K80@TQFP64(ISP) [DX0001]
PIC18F65K90(HVISP)(Disable) [DX0001]
PIC18F65K90(HVISP)(Enable) [DX0001]
PIC18F65K90(LVISP)(Disable) [DX0001]
PIC18F65K90(LVISP)(Enable) [DX0001]
PIC18F65K90@TQFP64(HV) [DX3011]
PIC18F65K90@TQFP64(LV) [DX3011]
PIC18F6620@TQFP64 [DX3011]
PIC18F6620@TQFP64(ISP) [DX0001]
PIC18F6621@TQFP64 [DX3011]
PIC18F6621@TQFP64(ISP) [DX0001]
PIC18F6622@TQFP64 [DX3011]
PIC18F6622@TQFP64(ISP)(High-V) [DX0001]
PIC18F6622@TQFP64(ISP)(Low-V) [DX0001]
PIC18F6627@TQFP64 [DX3011]
PIC18F6627@TQFP64(ISP)(High-V) [DX0001]
PIC18F6627@TQFP64(ISP)(Low-V) [DX0001]
PIC18F6628@TQFP64 [DX3011]
PIC18F6628@TQFP64(ISP)(High-V) [DX0001]
PIC18F6628@TQFP64(ISP)(Low-V) [DX0001]
PIC18F6680@PLCC68 [DX2068]
PIC18F6680@PLCC68(ISP) [DX0001]

PIC18F6680@TQFP64 [DX3011] PIC18F6680@TQFP64(ISP) [DX0001]
PIC18F66J10@TQFP64 [DX3011] PIC18F66J10@TQFP64(ISP) [DX0001]
PIC18F66J10@TQFP64(ISP)(Enable) [DX0001]
PIC18F66J11@TQFP64 [DX3011] PIC18F66J11@TQFP64(ISP) [DX0001]
PIC18F66J15@TQFP64 [DX3011] PIC18F66J15@TQFP64(ISP) [DX0001]
PIC18F66J15@TQFP64(ISP)(Enable) [DX0001]
PIC18F66J16@TQFP64 [DX3011] PIC18F66J16@TQFP64(ISP) [DX0001]
PIC18F66J50@TQFP64 [DX3011] PIC18F66J50@TQFP64(ISP) [DX0001]
PIC18F66J55@TQFP64 [DX3011] PIC18F66J55@TQFP64(ISP) [DX0001]
PIC18F66J60@TQFP64 [DX3011] PIC18F66J60@TQFP64(ISP) [DX0001]
PIC18F66J65@TQFP64 [DX3011] PIC18F66J65@TQFP64(ISP) [DX0001]
PIC18F66J90@TQFP64 [DX3011] PIC18F66J90@TQFP64(ISP) [DX0001]
PIC18F66J93@TQFP64 [DX3011] PIC18F66J93@TQFP64(ISP) [DX0001]
PIC18F66K22(HVISP)(Disable) [DX0001]
PIC18F66K22(HVISP)(Enable) [DX0001]
PIC18F66K22(LVISP)(Disable) [DX0001]
PIC18F66K22(LVISP)(Enable) [DX0001]
PIC18F66K22@TQFP64(HV) [DX3011] PIC18F66K22@TQFP64(LV) [DX3011]
PIC18F66K80@QFN64 [DX4023] PIC18F66K80@QFN64(ISP) [DX0001]
PIC18F66K80@TQFP64 [DX3011] PIC18F66K80@TQFP64(ISP) [DX0001]
PIC18F66K90(HVISP)(Disable) [DX0001]
PIC18F66K90(HVISP)(Enable) [DX0001]
PIC18F66K90(LVISP)(Disable) [DX0001]
PIC18F66K90(LVISP)(Enable) [DX0001]
PIC18F66K90@TQFP64(HV) [DX3011] PIC18F66K90@TQFP64(LV) [DX3011]
PIC18F6720@TQFP64 [DX3011] PIC18F6720@TQFP64(ISP) [DX0001]
PIC18F6720@TQFP64(MEXICO) [DX3011]
PIC18F6722@TQFP64 [DX3011]
PIC18F6722@TQFP64(ISP)(High-V) [DX0001]
PIC18F6722@TQFP64(ISP)(Low-V) [DX0001]
PIC18F6723@TQFP64 [DX3011]
PIC18F6723@TQFP64(ISP)(High-V) [DX0001]
PIC18F6723@TQFP64(ISP)(Low-V) [DX0001]
PIC18F67J10@TQFP64 [DX3011] PIC18F67J10@TQFP64(ISP) [DX0001]
PIC18F67J10@TQFP64(ISP)(Enable) [DX0001]
PIC18F67J11@TQFP64 [DX3011] PIC18F67J11@TQFP64(ISP) [DX0001]
PIC18F67J50@TQFP64 [DX3011] PIC18F67J50@TQFP64(ISP) [DX0001]
PIC18F67J60@TQFP64 [DX3011] PIC18F67J60@TQFP64(ISP) [DX0001]
PIC18F67J90@TQFP64 [DX3011] PIC18F67J90@TQFP64(ISP) [DX0001]
PIC18F67J93@TQFP64 [DX3011] PIC18F67J93@TQFP64(ISP) [DX0001]
PIC18F67K22(HVISP)(Disable) [DX0001]
PIC18F67K22(HVISP)(Enable) [DX0001]
PIC18F67K22(LVISP)(Disable) [DX0001]
PIC18F67K22(LVISP)(Enable) [DX0001]
PIC18F67K22@TQFP64(HV) [DX3011] PIC18F67K22@TQFP64(LV) [DX3011]
PIC18F67K90(HVISP)(Disable) [DX0001]
PIC18F67K90(HVISP)(Enable) [DX0001]
PIC18F67K90(LVISP)(Disable) [DX0001]

PIC18F67K90(LVISP)(Enable) [DX0001]
PIC18F67K90@TQFP64(HV) [DX3011]　　PIC18F67K90@TQFP64(LV) [DX3011]
PIC18F8310@TQFP80 [DX3016]　　PIC18F8310@TQFP80(ISP) [DX0001]
PIC18F8390@TQFP80 [DX3016]　　PIC18F8390@TQFP80(ISP) [DX0001]
PIC18F8393@TQFP80 [DX3016]　　PIC18F8393@TQFP80(ISP) [DX0001]
PIC18F83J11@TQFP80 [DX3060]　　PIC18F83J11@TQFP80(ISP) [DX0001]
PIC18F83J90@TQFP80 [DX3060]　　PIC18F83J90@TQFP80(ISP) [DX0001]
PIC18F8410@TQFP80 [DX3016]　　PIC18F8410@TQFP80(ISP) [DX0001]
PIC18F8490@TQFP80 [DX3016]　　PIC18F8490@TQFP80(ISP) [DX0001]
PIC18F8493@TQFP80 [DX3016]　　PIC18F8493@TQFP80(ISP) [DX0001]
PIC18F84J11@TQFP80 [DX3060]　　PIC18F84J11@TQFP80(ISP) [DX0001]
PIC18F84J90@TQFP80 [DX3060]　　PIC18F84J90@TQFP80(ISP) [DX0001]
PIC18F8520@TQFP80 [DX3016]　　PIC18F8520@TQFP80(ISP) [DX0001]
PIC18F8525@TQFP80 [DX3016]　　PIC18F8525@TQFP80(ISP) [DX0001]
PIC18F8527@TQFP80 [DX3016]
PIC18F8527@TQFP80(ISP)(High-V) [DX0001]
PIC18F8527@TQFP80(ISP)(Low-V) [DX0001]
PIC18F8585@TQFP80 [DX3016]　　PIC18F8585@TQFP80(ISP) [DX0001]
PIC18F85J10@TQFP80 [DX3060]　　PIC18F85J10@TQFP80(ISP) [DX0001]
PIC18F85J10@TQFP80(ISP)(Enable) [DX0001]
PIC18F85J11@TQFP80 [DX3060]　　PIC18F85J11@TQFP80(ISP) [DX0001]
PIC18F85J15@TQFP80 [DX3060]　　PIC18F85J15@TQFP80(ISP) [DX0001]
PIC18F85J15@TQFP80(ISP)(Enable) [DX0001]
PIC18F85J50@TQFP80 [DX3060]　　PIC18F85J50@TQFP80(ISP) [DX0001]
PIC18F85J90@TQFP80 [DX3060]　　PIC18F85J90@TQFP80(ISP) [DX0001]
PIC18F85K22(HVISP)(Disable) [DX0001]
PIC18F85K22(HVISP)(Enable) [DX0001]
PIC18F85K22(LVISP)(Disable) [DX0001]
PIC18F85K22(LVISP)(Enable) [DX0001]
PIC18F85K22@TQFP80(HV) [DX3016]　　PIC18F85K22@TQFP80(LV) [DX3016]
PIC18F85K90(HVISP)(Disable) [DX0001]
PIC18F85K90(HVISP)(Enable) [DX0001]
PIC18F85K90(LVISP)(Disable) [DX0001]
PIC18F85K90(LVISP)(Enable) [DX0001]
PIC18F85K90@TQFP80(HV) [DX3016]　　PIC18F85K90@TQFP80(LV) [DX3016]
PIC18F8620@TQFP80 [DX3016]　　PIC18F8620@TQFP80(ISP) [DX0001]
PIC18F8621@TQFP80 [DX3016]　　PIC18F8621@TQFP80(ISP) [DX0001]
PIC18F8622@TQFP80 [DX3016]
PIC18F8622@TQFP80(ISP)(High-V) [DX0001]
PIC18F8622@TQFP80(ISP)(Low-V) [DX0001]
PIC18F8627@TQFP80 [DX3016]
PIC18F8627@TQFP80(ISP)(High-V) [DX0001]
PIC18F8627@TQFP80(ISP)(Low-V) [DX0001]
PIC18F8628@TQFP80 [DX3016]
PIC18F8628@TQFP80(ISP)(High-V) [DX0001]
PIC18F8628@TQFP80(ISP)(Low-V) [DX0001]
PIC18F8680@TQFP80 [DX3016]　　PIC18F8680@TQFP80(ISP) [DX0001]
PIC18F86J10@TQFP80 [DX3060]　　PIC18F86J10@TQFP80(ISP) [DX0001]

PIC18F86J10@TQFP80(ISP)(Enable) [DX0001]
PIC18F86J11@TQFP80 [DX3060]　　PIC18F86J11@TQFP80(ISP) [DX0001]
PIC18F86J15@TQFP80 [DX3060]　　PIC18F86J15@TQFP80(ISP) [DX0001]
PIC18F86J15@TQFP80(ISP)(Enable) [DX0001]
PIC18F86J16@TQFP80 [DX3060]　　PIC18F86J16@TQFP80(ISP) [DX0001]
PIC18F86J50@TQFP80 [DX3060]　　PIC18F86J50@TQFP80(ISP) [DX0001]
PIC18F86J55@TQFP80 [DX3060]　　PIC18F86J55@TQFP80(ISP) [DX0001]
PIC18F86J60@TQFP80 [DX3060]　　PIC18F86J60@TQFP80(ISP) [DX0001]
PIC18F86J65@TQFP80 [DX3060]　　PIC18F86J65@TQFP80(ISP) [DX0001]
PIC18F86J72@TQFP80 [DX3060]　　PIC18F86J72@TQFP80(ISP) [DX0001]
PIC18F86J72@TQFP80(ISP)(Enable) [DX0001]
PIC18F86J90@TQFP80 [DX3060]　　PIC18F86J90@TQFP80(ISP) [DX0001]
PIC18F86J93@TQFP80 [DX3060]　　PIC18F86J93@TQFP80(ISP) [DX0001]
PIC18F86K22(HVISP)(Disable) [DX0001]
PIC18F86K22(HVISP)(Enable) [DX0001]
PIC18F86K22(LVISP)(Disable) [DX0001]
PIC18F86K22(LVISP)(Enable) [DX0001]
PIC18F86K22@TQFP80(HV) [DX3016]　　PIC18F86K22@TQFP80(LV) [DX3016]
PIC18F86K90(HVISP)(Disable) [DX0001]
PIC18F86K90(HVISP)(Enable) [DX0001]
PIC18F86K90(LVISP)(Disable) [DX0001]
PIC18F86K90(LVISP)(Enable) [DX0001]
PIC18F86K90@TQFP80(HV) [DX3016]　　PIC18F86K90@TQFP80(LV) [DX3016]
PIC18F8720@TQFP80 [DX3016]　　PIC18F8720@TQFP80(ISP) [DX0001]
PIC18F8722@TQFP80 [DX3016]
PIC18F8722@TQFP80(ISP)(High-V) [DX0001]
PIC18F8722@TQFP80(ISP)(Low-V) [DX0001]
PIC18F8723@TQFP80 [DX3016]
PIC18F8723@TQFP80(ISP)(High-V) [DX0001]
PIC18F8723@TQFP80(ISP)(Low-V) [DX0001]
PIC18F87J10@TQFP80 [DX3060]　　PIC18F87J10@TQFP80(ISP) [DX0001]
PIC18F87J10@TQFP80(ISP)(Enable) [DX0001]
PIC18F87J11@TQFP80 [DX3060]　　PIC18F87J11@TQFP80(ISP) [DX0001]
PIC18F87J50@TQFP80 [DX3060]　　PIC18F87J50@TQFP80(ISP) [DX0001]
PIC18F87J60@TQFP80 [DX3060]　　PIC18F87J60@TQFP80(ISP) [DX0001]
PIC18F87J72@TQFP80 [DX3060]　　PIC18F87J72@TQFP80(ISP) [DX0001]
PIC18F87J72@TQFP80(ISP)(Enable) [DX0001]
PIC18F87J90@TQFP80 [DX3060]　　PIC18F87J90@TQFP80(ISP) [DX0001]
PIC18F87J93@TQFP80 [DX3060]　　PIC18F87J93@TQFP80(ISP) [DX0001]
PIC18F87K22(HVISP)(Disable) [DX0001]
PIC18F87K22(HVISP)(Enable) [DX0001]
PIC18F87K22(LVISP)(Disable) [DX0001]
PIC18F87K22(LVISP)(Enable) [DX0001]
PIC18F87K22@TQFP80(HV) [DX3016]　　PIC18F87K22@TQFP80(LV) [DX3016]
PIC18F87K90(HVISP)(Disable) [DX0001]
PIC18F87K90(HVISP)(Enable) [DX0001]
PIC18F87K90(LVISP)(Disable) [DX0001]
PIC18F87K90(LVISP)(Enable) [DX0001]

PIC18F87K90@TQFP80(HV) [DX3016]　　PIC18F87K90@TQFP80(LV) [DX3016]
PIC18F96J60@TQFP100(ISP) [DX0001]
PIC18F96J60@TQFP100[12*12*1] [DX3071]
PIC18F96J60@TQFP100[14*14*1] [DX3021]
PIC18F96J65@TQFP100(ISP) [DX0001]
PIC18F96J65@TQFP100[12*12*1] [DX3071]
PIC18F96J65@TQFP100[14*14*1] [DX3021]
PIC18F97J60@TQFP100(ISP) [DX0001]
PIC18F97J60@TQFP100[12*12*1] [DX3071]
PIC18F97J60@TQFP100[14*14*1] [DX3021]
PIC18LC452 [DX0001]　　PIC18LC452@PLCC44 [DX2044]
PIC18LC452@TQFP44 [DX3003]　　PIC18LF1220 [DX0001]
PIC18LF1220(ISP) [DX0001]　　PIC18LF1220@QFN28 [DX4014]
PIC18LF1220@SOIC18 [DX1033]　　PIC18LF1220@SOIC18(ISP) [DX0001]
PIC18LF1220@SSOP20 [DX1026]　　PIC18LF1220@SSOP20(ISP) [DX0001]
PIC18LF1320 [DX0001]　　PIC18LF1320(ISP) [DX0001]
PIC18LF1320@QFN28 [DX4014]　　PIC18LF1320@SOIC18 [DX1033]
PIC18LF1320@SOIC18(ISP) [DX0001]　　PIC18LF1320@SSOP20 [DX1026]
PIC18LF1320@SSOP20(ISP) [DX0001]　　PIC18LF13K22 [DX0001]
PIC18LF13K22(ISP)(High-V) [DX0001]
PIC18LF13K22(ISP)(Low-V) [DX0001]
PIC18LF13K22@QFN20 [DX4011]
PIC18LF13K22@QFN20(ISP)(High-V) [DX0001]
PIC18LF13K22@QFN20(ISP)(Low-V) [DX0001]
PIC18LF13K22@SOIC20 [DX1033]
PIC18LF13K22@SOIC20(ISP)(High-V) [DX0001]
PIC18LF13K22@SOIC20(ISP)(Low-V) [DX0001]
PIC18LF13K22@SSOP20 [DX1026]
PIC18LF13K22@SSOP20(ISP)(High-V) [DX0001]
PIC18LF13K22@SSOP20(ISP)(Low-V) [DX0001]
PIC18LF13K50 [DX0001]
PIC18LF13K50(ISP)(High-V) [DX0001]
PIC18LF13K50(ISP)(Low-V) [DX0001]
PIC18LF13K50@QFN20 [DX4025]
PIC18LF13K50@QFN20(ISP)(High-V) [DX0001]
PIC18LF13K50@QFN20(ISP)(Low-V) [DX0001]
PIC18LF13K50@SOIC20 [DX1033]
PIC18LF13K50@SOIC20(ISP)(High-V) [DX0001]
PIC18LF13K50@SOIC20(ISP)(Low-V) [DX0001]
PIC18LF13K50@SSOP20 [DX1026]
PIC18LF13K50@SSOP20(ISP)(High-V) [DX0001]
PIC18LF13K50@SSOP20(ISP)(Low-V) [DX0001]
PIC18LF14K22 [DX0001]
PIC18LF14K22(ISP)(High-V) [DX0001]
PIC18LF14K22(ISP)(Low-V) [DX0001]
PIC18LF14K22@QFN20 [DX4011]
PIC18LF14K22@QFN20(ISP)(High-V) [DX0001]
PIC18LF14K22@QFN20(ISP)(Low-V) [DX0001]

PIC18LF14K22@SOIC20 [DX1033]
PIC18LF14K22@SOIC20(ISP)(High-V) [DX0001]
PIC18LF14K22@SOIC20(ISP)(Low-V) [DX0001]
PIC18LF14K22@SSOP20 [DX1026]
PIC18LF14K22@SSOP20(ISP)(High-V) [DX0001]
PIC18LF14K22@SSOP20(ISP)(Low-V) [DX0001]
PIC18LF14K50 [DX0001]
PIC18LF14K50(ISP)(High-V) [DX0001]
PIC18LF14K50(ISP)(Low-V) [DX0001]
PIC18LF14K50@QFN20 [DX4025]
PIC18LF14K50@QFN20(ISP)(High-V) [DX0001]
PIC18LF14K50@QFN20(ISP)(Low-V) [DX0001]
PIC18LF14K50@SOIC20 [DX1033]
PIC18LF14K50@SOIC20(ISP)(High-V) [DX0001]
PIC18LF14K50@SOIC20(ISP)(Low-V) [DX0001]
PIC18LF14K50@SSOP20 [DX1026]
PIC18LF14K50@SSOP20(ISP)(High-V) [DX0001]
PIC18LF14K50@SSOP20(ISP)(Low-V) [DX0001]
PIC18LF2220 [DX0001]　　PIC18LF2220(ISP) [DX0001]
PIC18LF2220@SOIC28 [DX1033]　　PIC18LF2220@SOIC28(ISP) [DX0001]
PIC18LF2221 [DX0001]　　PIC18LF2221(ISP)(Low-V) [DX0001]
PIC18LF2221@QFN28 [DX4014]
PIC18LF2221@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2221@SOIC28 [DX1033]
PIC18LF2221@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2221@SSOP28 [DX1026]
PIC18LF2221@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2320 [DX0001]　　PIC18LF2320(ISP) [DX0001]
PIC18LF2320@SOIC28 [DX1033]　　PIC18LF2320@SOIC28(ISP) [DX0001]
PIC18LF2321 [DX0001]　　PIC18LF2321(ISP)(Low-V) [DX0001]
PIC18LF2321@QFN28 [DX4014]
PIC18LF2321@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2321@SOIC28 [DX1033]
PIC18LF2321@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2321@SSOP28 [DX1026]
PIC18LF2321@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2331 [DX0001]　　PIC18LF2331(ISP) [DX0001]
PIC18LF2331@SOIC28 [DX1033]　　PIC18LF2331@SOIC28(ISP) [DX0001]
PIC18LF23K22 [DX0001]　　PIC18LF23K22(ISP)(H-V) [DX0001]
PIC18LF23K22@QFN28 [DX4014]
PIC18LF23K22@QFN28(ISP)(H-V) [DX0001]
PIC18LF23K22@SOIC28 [DX1033]
PIC18LF23K22@SOIC28(ISP)(H-V) [DX0001]
PIC18LF23K22@SSOP28 [DX1077]
PIC18LF23K22@SSOP28(ISP)(H-V) [DX0001]
PIC18LF23K22@UQFN28 [DX4036]　　PIC18LF2410 [DX0001]
PIC18LF2410(ISP)(Low-V) [DX0001]　　PIC18LF2410@QFN28 [DX4014]
PIC18LF2410@QFN28(ISP)(Low-V) [DX0001]

PIC18LF2410@SOIC28 [DX1033]
PIC18LF2410@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2410@SSOP28 [DX1026]
PIC18LF2410@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF242 [DX0001]
PIC18LF242(ISP) [DX0001]
PIC18LF242@SOIC28 [DX1033]
PIC18LF242@SOIC28(ISP) [DX0001]
PIC18LF2420 [DX0001]
PIC18LF2420(ISP)(High-V) [DX0001]
PIC18LF2420(ISP)(Low-V) [DX0001]
PIC18LF2420@QFN28 [DX4014]
PIC18LF2420@QFN28(ISP)(High-V) [DX0001]
PIC18LF2420@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2420@SOIC28 [DX1033]
PIC18LF2420@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2420@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2420@SSOP28 [DX1026]
PIC18LF2420@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2420@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2423 [DX0001]
PIC18LF2423(ISP)(High-V) [DX0001]
PIC18LF2423(ISP)(Low-V) [DX0001]
PIC18LF2423@QFN28 [DX4014]
PIC18LF2423@QFN28(ISP)(High-V) [DX0001]
PIC18LF2423@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2423@SOIC28 [DX1033]
PIC18LF2423@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2423@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2423@SSOP28 [DX1026]
PIC18LF2423@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2423@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2431 [DX0001]
PIC18LF2431(ISP) [DX0001]
PIC18LF2431@SOIC28 [DX1033]
PIC18LF2431@SOIC28(ISP) [DX0001]
PIC18LF2439 [DX0001]
PIC18LF2439(ISP) [DX0001]
PIC18LF2439@SOIC28 [DX1033]
PIC18LF2439@SOIC28(ISP) [DX0001]
PIC18LF2450 [DX0001]
PIC18LF2450(ISP)(Low-V) [DX0001]
PIC18LF2450@QFN28 [DX4014]
PIC18LF2450@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2450@SOIC28 [DX1033]
PIC18LF2450@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2450@SSOP28 [DX1026]
PIC18LF2450@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2455 [DX0001]
PIC18LF2455(ISP)(High-V) [DX0001]
PIC18LF2455(ISP)(Low-V) [DX0001]
PIC18LF2455@SOIC28 [DX1033]
PIC18LF2455@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2455@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2455@SSOP28 [DX1026]
PIC18LF2455@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2455@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF248 [DX0001]
PIC18LF248(ISP) [DX0001]

PIC18LF248@SOIC28 [DX1033]　　PIC18LF248@SOIC28(ISP) [DX0001]
PIC18LF2480 [DX0001]
PIC18LF2480(ISP)(High-V) [DX0001]
PIC18LF2480(ISP)(Low-V) [DX0001]　　PIC18LF2480@QFN28 [DX4014]
PIC18LF2480@QFN28(ISP)(High-V) [DX0001]
PIC18LF2480@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2480@SOIC28 [DX1033]
PIC18LF2480@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2480@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2480@SSOP28 [DX1026]
PIC18LF2480@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2480@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF24J10 [DX0001]　　PIC18LF24J10(ISP) [DX0001]
PIC18LF24J10@QFN28 [DX4014]　　PIC18LF24J10@QFN28(ISP) [DX0001]
PIC18LF24J10@SOIC28 [DX1033]
PIC18LF24J10@SOIC28(ISP) [DX0001]
PIC18LF24J10@SSOP28 [DX1026]
PIC18LF24J10@SSOP28(ISP) [DX0001]
PIC18LF24J11 [DX0001]　　PIC18LF24J11(ISP) [DX0001]
PIC18LF24J11@QFN28 [DX4014]　　PIC18LF24J11@QFN28(ISP) [DX0001]
PIC18LF24J11@SOIC28 [DX1033]
PIC18LF24J11@SOIC28(ISP) [DX0001]
PIC18LF24J11@SSOP28 [DX1026]
PIC18LF24J11@SSOP28(ISP) [DX0001]
PIC18LF24J50 [DX0001]　　PIC18LF24J50(ISP) [DX0001]
PIC18LF24J50@QFN28 [DX4014]　　PIC18LF24J50@QFN28(ISP) [DX0001]
PIC18LF24J50@SOIC28 [DX1033]
PIC18LF24J50@SOIC28(ISP) [DX0001]
PIC18LF24J50@SSOP28 [DX1026]
PIC18LF24J50@SSOP28(ISP) [DX0001]
PIC18LF24K22 [DX0001]　　PIC18LF24K22(ISP)(H-V) [DX0001]
PIC18LF24K22@QFN28 [DX4014]
PIC18LF24K22@QFN28(ISP)(H-V) [DX0001]
PIC18LF24K22@SOIC28 [DX1033]
PIC18LF24K22@SOIC28(ISP)(H-V) [DX0001]
PIC18LF24K22@SSOP28 [DX1077]
PIC18LF24K22@SSOP28(ISP)(H-V) [DX0001]
PIC18LF24K22@UQFN28 [DX4036]　　PIC18LF24K50 [DX0001]
PIC18LF24K50@ISP [DX0001]　　PIC18LF24K50@QFN28 [DX4014]
PIC18LF24K50@SOIC28 [DX1033]　　PIC18LF24K50@SSOP28 [DX1077]
PIC18LF2510 [DX0001]　　PIC18LF2510(ISP) [DX0001]
PIC18LF2510@QFN28 [DX4014]　　PIC18LF2510@QFN28(ISP) [DX0001]
PIC18LF2510@SOIC28 [DX1033]　　PIC18LF2510@SOIC28(ISP) [DX0001]
PIC18LF2510@SSOP28 [DX1026]　　PIC18LF2510@SSOP28(ISP) [DX0001]
PIC18LF2515 [DX0001]　　PIC18LF2515(ISP)(Low-V) [DX0001]
PIC18LF2515@SOIC28 [DX1033]
PIC18LF2515@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2515@SSOP28 [DX1026]

PIC18LF2515@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF252 [DX0001]
PIC18LF252(ISP) [DX0001]
PIC18LF252@SOIC28 [DX1033]
PIC18LF252@SOIC28(ISP) [DX0001]
PIC18LF2520 [DX0001]
PIC18LF2520(ISP)(High-V) [DX0001]
PIC18LF2520(ISP)(Low-V) [DX0001]
PIC18LF2520@QFN28 [DX4014]
PIC18LF2520@QFN28(ISP)(High-V) [DX0001]
PIC18LF2520@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2520@SOIC28 [DX1033]
PIC18LF2520@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2520@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2520@SSOP28 [DX1026]
PIC18LF2520@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2520@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2523 [DX0001]
PIC18LF2523(ISP)(High-V) [DX0001]
PIC18LF2523(ISP)(Low-V) [DX0001]
PIC18LF2523@QFN28 [DX4014]
PIC18LF2523@QFN28(ISP)(High-V) [DX0001]
PIC18LF2523@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2523@SOIC28 [DX1033]
PIC18LF2523@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2523@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2523@SSOP28 [DX1026]
PIC18LF2523@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2523@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2525 [DX0001]
PIC18LF2525(ISP)(Low-V) [DX0001]
PIC18LF2525@SOIC28 [DX1033]
PIC18LF2525@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2525@SSOP28 [DX1026]
PIC18LF2525@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2539 [DX0001]
PIC18LF2539(ISP) [DX0001]
PIC18LF2539@SOIC28 [DX1033]
PIC18LF2539@SOIC28(ISP) [DX0001]
PIC18LF2550 [DX0001]
PIC18LF2550(ISP)(High-V) [DX0001]
PIC18LF2550(ISP)(Low-V) [DX0001]
PIC18LF2550@SOIC28 [DX1033]
PIC18LF2550@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2550@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2550@SSOP28 [DX1026]
PIC18LF2550@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2550@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF258 [DX0001]
PIC18LF258(ISP) [DX0001]
PIC18LF258@SOIC28 [DX1033]
PIC18LF258@SOIC28(ISP) [DX0001]
PIC18LF2580 [DX0001]
PIC18LF2580(ISP)(High-V) [DX0001]
PIC18LF2580(ISP)(Low-V) [DX0001]
PIC18LF2580@QFN28 [DX4014]
PIC18LF2580@QFN28(ISP)(High-V) [DX0001]
PIC18LF2580@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2580@SOIC28 [DX1033]

PIC18LF2580@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2580@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2580@SSOP28 [DX1026]
PIC18LF2580@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2580@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2585 [DX0001]
PIC18LF2585(ISP)(High-V) [DX0001]
PIC18LF2585(ISP)(Low-V) [DX0001] PIC18LF2585@SDIP28 [DX0032]
PIC18LF2585@SDIP28(ISP)(High-V) [DX0001]
PIC18LF2585@SDIP28(ISP)(Low-V) [DX0001]
PIC18LF2585@SOIC28 [DX1033]
PIC18LF2585@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2585@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2585@SSOP28 [DX1026]
PIC18LF2585@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2585@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF25J10 [DX0001] PIC18LF25J10(ISP) [DX0001]
PIC18LF25J10@QFN28 [DX4014] PIC18LF25J10@QFN28(ISP) [DX0001]
PIC18LF25J10@SOIC28 [DX1033]
PIC18LF25J10@SOIC28(ISP) [DX0001]
PIC18LF25J10@SSOP28 [DX1026]
PIC18LF25J10@SSOP28(ISP) [DX0001]
PIC18LF25J11 [DX0001] PIC18LF25J11(ISP) [DX0001]
PIC18LF25J11@QFN28 [DX4014] PIC18LF25J11@QFN28(ISP) [DX0001]
PIC18LF25J11@SOIC28 [DX1033]
PIC18LF25J11@SOIC28(ISP) [DX0001]
PIC18LF25J11@SSOP28 [DX1026]
PIC18LF25J11@SSOP28(ISP) [DX0001]
PIC18LF25J50 [DX0001] PIC18LF25J50(ISP) [DX0001]
PIC18LF25J50@QFN28 [DX4014] PIC18LF25J50@QFN28(ISP) [DX0001]
PIC18LF25J50@SOIC28 [DX1033]
PIC18LF25J50@SOIC28(ISP) [DX0001]
PIC18LF25J50@SSOP28 [DX1026]
PIC18LF25J50@SSOP28(ISP) [DX0001]
PIC18LF25K22 [DX0001] PIC18LF25K22(ISP)(H-V) [DX0001]
PIC18LF25K22@QFN28 [DX4014]
PIC18LF25K22@QFN28(ISP)(H-V) [DX0001]
PIC18LF25K22@SOIC28 [DX1033]
PIC18LF25K22@SOIC28(ISP)(H-V) [DX0001]
PIC18LF25K22@SSOP28 [DX1077]
PIC18LF25K22@SSOP28(ISP)(H-V) [DX0001]
PIC18LF25K22@UQFN28 [DX4036] PIC18LF25K50 [DX0001]
PIC18LF25K50@ISP [DX0001] PIC18LF25K50@QFN28 [DX4014]
PIC18LF25K50@SOIC28 [DX1033] PIC18LF25K50@SSOP28 [DX1077]
PIC18LF25K80 [DX0001] PIC18LF25K80(ISP) [DX0001]
PIC18LF25K80@QFN28 [DX4014] PIC18LF25K80@QFN28(ISP) [DX0001]
PIC18LF25K80@SOIC28 [DX1033]
PIC18LF25K80@SOIC28(ISP) [DX0001]

PIC18LF25K80@SSOP28 [DX1026]
PIC18LF25K80@SSOP28(ISP) [DX0001]
PIC18LF2610 [DX0001]　　PIC18LF2610(ISP)(Low-V) [DX0001]
PIC18LF2610@SOIC28 [DX1033]
PIC18LF2610@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2610@SSOP28 [DX1026]
PIC18LF2610@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2620 [DX0001]　　PIC18LF2620(ISP)(Low-V) [DX0001]
PIC18LF2620@SOIC28 [DX1033]
PIC18LF2620@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2620@SSOP28 [DX1026]
PIC18LF2620@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2680 [DX0001]
PIC18LF2680(ISP)(High-V) [DX0001]
PIC18LF2680(ISP)(Low-V) [DX0001]　　PIC18LF2680@SDIP28 [DX0032]
PIC18LF2680@SDIP28(ISP)(High-V) [DX0001]
PIC18LF2680@SDIP28(ISP)(Low-V) [DX0001]
PIC18LF2680@SOIC28 [DX1033]
PIC18LF2680@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2680@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2680@SSOP28 [DX1026]
PIC18LF2680@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2680@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2682 [DX0001]
PIC18LF2682(ISP)(High-V) [DX0001]
PIC18LF2682(ISP)(Low-V) [DX0001]　　PIC18LF2682@QFN28 [DX4014]
PIC18LF2682@QFN28(ISP)(High-V) [DX0001]
PIC18LF2682@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2682@SOIC28 [DX1033]
PIC18LF2682@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2682@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2682@SSOP28 [DX1026]
PIC18LF2682@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2682@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF2685 [DX0001]
PIC18LF2685(ISP)(High-V) [DX0001]
PIC18LF2685(ISP)(Low-V) [DX0001]　　PIC18LF2685@QFN28 [DX4014]
PIC18LF2685@QFN28(ISP)(High-V) [DX0001]
PIC18LF2685@QFN28(ISP)(Low-V) [DX0001]
PIC18LF2685@SOIC28 [DX1033]
PIC18LF2685@SOIC28(ISP)(High-V) [DX0001]
PIC18LF2685@SOIC28(ISP)(Low-V) [DX0001]
PIC18LF2685@SSOP28 [DX1026]
PIC18LF2685@SSOP28(ISP)(High-V) [DX0001]
PIC18LF2685@SSOP28(ISP)(Low-V) [DX0001]
PIC18LF26J11 [DX0001]　　PIC18LF26J11(ISP) [DX0001]
PIC18LF26J11@QFN28 [DX4014]　　PIC18LF26J11@QFN28(ISP) [DX0001]
PIC18LF26J11@SOIC28 [DX1033]

PIC18LF26J11@SOIC28(ISP) [DX0001]
PIC18LF26J11@SSOP28 [DX1026]
PIC18LF26J11@SSOP28(ISP) [DX0001]
PIC18LF26J13 [DX0001]
PIC18LF26J13(ISP) [DX0001]
PIC18LF26J13@QFN28 [DX4014]
PIC18LF26J13@QFN28(ISP) [DX0001]
PIC18LF26J13@SOIC28 [DX1033]
PIC18LF26J13@SOIC28(ISP) [DX0001]
PIC18LF26J13@SSOP28 [DX1026]
PIC18LF26J13@SSOP28(ISP) [DX0001]
PIC18LF26J50 [DX0001]
PIC18LF26J50(ISP) [DX0001]
PIC18LF26J50@QFN28 [DX4014]
PIC18LF26J50@QFN28(ISP) [DX0001]
PIC18LF26J50@SOIC28 [DX1026]
PIC18LF26J50@SOIC28(ISP) [DX0001]
PIC18LF26J50@SSOP28
PIC18LF26J50@SSOP28(ISP) [DX0001]
PIC18LF26J53 [DX0001]
PIC18LF26J53(ISP) [DX0001]
PIC18LF26J53@QFN28 [DX4014]
PIC18LF26J53@QFN28(ISP) [DX0001]
PIC18LF26J53@SOIC28 [DX1033]
PIC18LF26J53@SOIC28(ISP) [DX0001]
PIC18LF26J53@SSOP28 [DX1026]
PIC18LF26J53@SSOP28(ISP) [DX0001]
PIC18LF26K22 [DX0001]
PIC18LF26K22(ISP)(H-V) [DX0001]
PIC18LF26K22@QFN28 [DX4014]
PIC18LF26K22@QFN28(ISP)(H-V) [DX0001]
PIC18LF26K22@SOIC28 [DX1033]
PIC18LF26K22@SOIC28(ISP)(H-V) [DX0001]
PIC18LF26K22@SSOP28 [DX1077]
PIC18LF26K22@SSOP28(ISP)(H-V) [DX0001]
PIC18LF26K22@UQFN28 [DX4036]
PIC18LF26K50 [DX0001]
PIC18LF26K50@ISP [DX0001]
PIC18LF26K50@QFN28 [DX4014]
PIC18LF26K50@SOIC28 [DX1033]
PIC18LF26K50@SSOP28 [DX1077]
PIC18LF26K80 [DX0001]
PIC18LF26K80(ISP) [DX0001]
PIC18LF26K80@QFN28 [DX4014]
PIC18LF26K80@QFN28(ISP) [DX0001]
PIC18LF26K80@SOIC28 [DX1033]
PIC18LF26K80@SOIC28(ISP) [DX0001]
PIC18LF26K80@SSOP28 [DX1026]
PIC18LF26K80@SSOP28(ISP) [DX0001]
PIC18LF27J13 [DX0001]
PIC18LF27J13(ISP) [DX0001]
PIC18LF27J13@QFN28 [DX4014]
PIC18LF27J13@QFN28(ISP) [DX0001]
PIC18LF27J13@SOIC28 [DX1033]
PIC18LF27J13@SOIC28(ISP) [DX0001]
PIC18LF27J13@SSOP28 [DX1026]
PIC18LF27J13@SSOP28(ISP) [DX0001]
PIC18LF27J53 [DX0001]
PIC18LF27J53(ISP) [DX0001]
PIC18LF27J53@QFN28 [DX4014]
PIC18LF27J53@QFN28(ISP) [DX0001]
PIC18LF27J53@SOIC28 [DX1033]
PIC18LF27J53@SOIC28(ISP) [DX0001]
PIC18LF27J53@SSOP28 [DX1026]

PIC18LF27J53@SSOP28(ISP) [DX0001]
PIC18LF4220 [DX0001]
PIC18LF4220(ISP) [DX0001]
PIC18LF4220@QFN44 [DX4018]
PIC18LF4220@QFN44(ISP) [DX0001]
PIC18LF4220@QFN44(ML) [DX4019]
PIC18LF4220@QFN44(ML)(ISP) [DX0001]
PIC18LF4220@TQFP44 [DX3003]
PIC18LF4220@TQFP44(ISP) [DX0001]
PIC18LF4221 [DX0001]
PIC18LF4221(ISP)(Low-V) [DX0001]
PIC18LF4221@QFN44 [DX4018]
PIC18LF4221@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4221@QFN44(ML) [DX4019]
PIC18LF4221@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4221@TQFP44 [DX3003]
PIC18LF4221@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4320 [DX0001]
PIC18LF4320(ISP) [DX0001]
PIC18LF4320@QFN44 [DX4018]
PIC18LF4320@QFN44(ISP) [DX0001]
PIC18LF4320@QFN44(ML) [DX4019]
PIC18LF4320@QFN44(ML)(ISP) [DX0001]
PIC18LF4320@TQFP44 [DX3003]
PIC18LF4320@TQFP44(ISP) [DX0001]
PIC18LF4321 [DX0001]
PIC18LF4321(ISP)(Low-V) [DX0001]
PIC18LF4321@QFN44 [DX4018]
PIC18LF4321@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4321@QFN44(ML) [DX4019]
PIC18LF4321@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4321@TQFP44 [DX3003]
PIC18LF4321@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4331 [DX0001]
PIC18LF4331(ISP) [DX0001]
PIC18LF4331@TQFP44 [DX3003]
PIC18LF4331@TQFP44(ISP) [DX0001]
PIC18LF43K22 [DX0001]
PIC18LF43K22(ISP)(H-V) [DX0001]
PIC18LF43K22@QFN44 [DX4018]
PIC18LF43K22@QFN44(ISP)(H-V) [DX0001]
PIC18LF43K22@QFN44(ML) [DX4019]
PIC18LF43K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF43K22@TQFP44 [DX3003]
PIC18LF43K22@TQFP44(ISP)(H-V) [DX0001]
PIC18LF43K22@UQFN40 [DX4039]
PIC18LF4410 [DX0001]
PIC18LF4410(ISP)(Low-V) [DX0001]
PIC18LF4410@QFN44 [DX4018]
PIC18LF4410@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4410@QFN44(ML) [DX4019]
PIC18LF4410@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4410@TQFP44 [DX3003]
PIC18LF4410@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF442 [DX0001]
PIC18LF442(ISP) [DX0001]
PIC18LF442@PLCC44 [DX2044]
PIC18LF442@PLCC44(ISP) [DX0001]
PIC18LF442@QFN44 [DX4019]
PIC18LF442@TQFP44 [DX3003]
PIC18LF442@TQFP44(ISP) [DX0001]
PIC18LF4420 [DX0001]
PIC18LF4420(ISP)(Low-V) [DX0001]
PIC18LF4420@QFN44 [DX4018]
PIC18LF4420@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4420@QFN44(ML) [DX4019]

PIC18LF4420@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4420@TQFP44 [DX3003]
PIC18LF4420@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4423 [DX0001]
PIC18LF4423(ISP)(High-V) [DX0001]
PIC18LF4423(ISP)(Low-V) [DX0001] PIC18LF4423@QFN44 [DX4018]
PIC18LF4423@QFN44(ISP)(High-V) [DX0001]
PIC18LF4423@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4423@QFN44(ML) [DX4019]
PIC18LF4423@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4423@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4423@TQFP44 [DX3003]
PIC18LF4423@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4423@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4431 [DX0001] PIC18LF4431(ISP) [DX0001]
PIC18LF4431@TQFP44 [DX3003] PIC18LF4431@TQFP44(ISP) [DX0001]
PIC18LF4439 [DX0001] PIC18LF4439(ISP) [DX0001]
PIC18LF4439@TQFP44 [DX3003] PIC18LF4439@TQFP44(ISP) [DX0001]
PIC18LF4450 [DX0001] PIC18LF4450(ISP)(Low-V) [DX0001]
PIC18LF4450@QFN44 [DX4018]
PIC18LF4450@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4450@QFN44(ML) [DX4019]
PIC18LF4450@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4450@TQFP44 [DX3003]
PIC18LF4450@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4455 [DX0001]
PIC18LF4455(ISP)(High-V) [DX0001]
PIC18LF4455(ISP)(Low-V) [DX0001] PIC18LF4455@QFN44 [DX4018]
PIC18LF4455@QFN44(ISP)(High-V) [DX0001]
PIC18LF4455@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4455@QFN44(ML) [DX4019]
PIC18LF4455@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4455@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4455@TQFP44 [DX3003]
PIC18LF4455@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4455@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF448 [DX0001] PIC18LF448(ISP) [DX0001]
PIC18LF448@PLCC44 [DX2044] PIC18LF448@PLCC44(ISP) [DX0001]
PIC18LF448@QFN44 [DX4019] PIC18LF448@TQFP44 [DX3003]
PIC18LF448@TQFP44(ISP) [DX0001] PIC18LF4480 [DX0001]
PIC18LF4480(ISP)(High-V) [DX0001]
PIC18LF4480(ISP)(Low-V) [DX0001] PIC18LF4480@QFN44 [DX4018]
PIC18LF4480@QFN44(ISP)(High-V) [DX0001]
PIC18LF4480@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4480@QFN44(ML) [DX4019]
PIC18LF4480@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4480@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4480@TQFP44 [DX3003]

PIC18LF4480@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4480@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF44J10 [DX0001]
PIC18LF44J10(ISP) [DX0001]
PIC18LF44J10@QFN44 [DX4018]
PIC18LF44J10@QFN44(ISP) [DX0001]
PIC18LF44J10@QFN44(ML) [DX4019]
PIC18LF44J10@QFN44(ML)(ISP) [DX0001]
PIC18LF44J10@TQFP44 [DX3003]
PIC18LF44J10@TQFP44(ISP) [DX0001]
PIC18LF44J11 [DX0001]
PIC18LF44J11(ISP) [DX0001]
PIC18LF44J11@QFN44 [DX4018]
PIC18LF44J11@QFN44(ISP) [DX0001]
PIC18LF44J11@QFN44(ML) [DX4019]
PIC18LF44J11@QFN44(ML)(ISP) [DX0001]
PIC18LF44J11@TQFP44 [DX3003]
PIC18LF44J11@TQFP44(ISP) [DX0001]
PIC18LF44J50 [DX0001]
PIC18LF44J50(ISP) [DX0001]
PIC18LF44J50@QFN44 [DX4018]
PIC18LF44J50@QFN44(ISP) [DX0001]
PIC18LF44J50@QFN44(ML) [DX4019]
PIC18LF44J50@QFN44(ML)(ISP) [DX0001]
PIC18LF44J50@TQFP44 [DX3003]
PIC18LF44J50@TQFP44(ISP) [DX0001]
PIC18LF44K22 [DX0001]
PIC18LF44K22(ISP)(H-V) [DX0001]
PIC18LF44K22@QFN44 [DX4018]
PIC18LF44K22@QFN44(ISP)(H-V) [DX0001]
PIC18LF44K22@QFN44(ML) [DX4019]
PIC18LF44K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF44K22@TQFP44 [DX3003]
PIC18LF44K22@TQFP44(ISP)(H-V) [DX0001]
PIC18LF44K22@UQFN40 [DX4039]
PIC18LF4510 [DX0001]
PIC18LF4510(ISP) [DX0001]
PIC18LF4510@QFN44 [DX4018]
PIC18LF4510@QFN44(ISP) [DX0001]
PIC18LF4510@QFN44(ML) [DX4019]
PIC18LF4510@QFN44(ML)(ISP) [DX0001]
PIC18LF4510@TQFP44 [DX3003]
PIC18LF4510@TQFP44(ISP) [DX0001]
PIC18LF4515 [DX0001]
PIC18LF4515(ISP)(Low-V) [DX0001]
PIC18LF4515@QFN44 [DX4018]
PIC18LF4515@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4515@QFN44(ML) [DX4019]
PIC18LF4515@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4515@TQFP44 [DX3003]
PIC18LF4515@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF452 [DX0001]
PIC18LF452(ISP) [DX0001]
PIC18LF452@PLCC44 [DX2044]
PIC18LF452@PLCC44(ISP) [DX0001]
PIC18LF452@QFN44 [DX4019]
PIC18LF452@TQFP44 [DX3003]
PIC18LF452@TQFP44(ISP) [DX0001]
PIC18LF4520 [DX0001]
PIC18LF4520(ISP) [DX0001]
PIC18LF4520@QFN44 [DX4018]
PIC18LF4520@QFN44(ISP) [DX0001]
PIC18LF4520@QFN44(ML) [DX4019]
PIC18LF4520@QFN44(ML)(ISP) [DX0001]
PIC18LF4520@TQFP44 [DX3003]
PIC18LF4520@TQFP44(ISP) [DX0001]
PIC18LF4523 [DX0001]

PIC18LF4523(ISP)(High-V) [DX0001]
PIC18LF4523(ISP)(Low-V) [DX0001] PIC18LF4523@QFN44 [DX4018]
PIC18LF4523@QFN44(ISP)(High-V) [DX0001]
PIC18LF4523@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4523@QFN44(ML) [DX4019]
PIC18LF4523@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4523@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4523@TQFP44 [DX3003]
PIC18LF4523@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4523@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4525 [DX0001] PIC18LF4525(ISP)(Low-V) [DX0001]
PIC18LF4525@QFN44 [DX4018]
PIC18LF4525@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4525@QFN44(ML) [DX4019]
PIC18LF4525@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4525@TQFP44 [DX3003]
PIC18LF4525@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4539 [DX0001] PIC18LF4539(ISP) [DX0001]
PIC18LF4539@TQFP44 [DX3003] PIC18LF4539@TQFP44(ISP) [DX0001]
PIC18LF4550 [DX0001]
PIC18LF4550(ISP)(High-V) [DX0001]
PIC18LF4550(ISP)(Low-V) [DX0001] PIC18LF4550@QFN44 [DX4018]
PIC18LF4550@QFN44(ISP)(High-V) [DX0001]
PIC18LF4550@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4550@QFN44(ML) [DX4019]
PIC18LF4550@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4550@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4550@TQFP44 [DX3003]
PIC18LF4550@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4550@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF458 [DX0001] PIC18LF458(ISP) [DX0001]
PIC18LF458@PLCC44 [DX2044] PIC18LF458@PLCC44(ISP) [DX0001]
PIC18LF458@QFN44 [DX4019] PIC18LF458@TQFP44 [DX3003]
PIC18LF458@TQFP44(ISP) [DX0001] PIC18LF4580 [DX0001]
PIC18LF4580(ISP)(High-V) [DX0001]
PIC18LF4580(ISP)(Low-V) [DX0001] PIC18LF4580@QFN44 [DX4018]
PIC18LF4580@QFN44(ISP)(High-V) [DX0001]
PIC18LF4580@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4580@QFN44(ML) [DX4019]
PIC18LF4580@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4580@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4580@TQFP44 [DX3003]
PIC18LF4580@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4580@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4585 [DX0001]
PIC18LF4585(ISP)(High-V) [DX0001]
PIC18LF4585(ISP)(Low-V) [DX0001] PIC18LF4585@QFN44 [DX4018]
PIC18LF4585@QFN44(ISP)(High-V) [DX0001]

PIC18LF4585@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4585@QFN44(ML) [DX4019]
PIC18LF4585@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4585@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4585@TQFP44 [DX3003]
PIC18LF4585@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4585@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF45J10 [DX0001]
PIC18LF45J10(ISP) [DX0001]
PIC18LF45J10@QFN44 [DX4018]
PIC18LF45J10@QFN44(ISP) [DX0001]
PIC18LF45J10@QFN44(ML) [DX4019]
PIC18LF45J10@QFN44(ML)(ISP) [DX0001]
PIC18LF45J10@TQFP44 [DX3003]
PIC18LF45J10@TQFP44(ISP) [DX0001]
PIC18LF45J11 [DX0001]
PIC18LF45J11(ISP) [DX0001]
PIC18LF45J11@QFN44 [DX4018]
PIC18LF45J11@QFN44(ISP) [DX0001]
PIC18LF45J11@QFN44(ML) [DX4019]
PIC18LF45J11@QFN44(ML)(ISP) [DX0001]
PIC18LF45J11@TQFP44 [DX3003]
PIC18LF45J11@TQFP44(ISP) [DX0001]
PIC18LF45J50 [DX0001]
PIC18LF45J50(ISP) [DX0001]
PIC18LF45J50@QFN44 [DX4018]
PIC18LF45J50@QFN44(ISP) [DX0001]
PIC18LF45J50@QFN44(ML) [DX4019]
PIC18LF45J50@QFN44(ML)(ISP) [DX0001]
PIC18LF45J50@TQFP44 [DX3003]
PIC18LF45J50@TQFP44(ISP) [DX0001]
PIC18LF45K22 [DX0001]
PIC18LF45K22(ISP)(H-V) [DX0001]
PIC18LF45K22@QFN44 [DX4018]
PIC18LF45K22@QFN44(ISP)(H-V) [DX0001]
PIC18LF45K22@QFN44(ML) [DX4019]
PIC18LF45K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF45K22@TQFP44 [DX3003]
PIC18LF45K22@TQFP44(ISP)(H-V) [DX0001]
PIC18LF45K22@UQFN40 [DX4039]
PIC18LF45K50 [DX0001]
PIC18LF45K50@ISP [DX0001]
PIC18LF45K50@QFN44 [DX4019]
PIC18LF45K50@TQFP44 [DX3003]
PIC18LF45K50@UQFN40 [DX4039]
PIC18LF45K80 [DX0001]
PIC18LF45K80(ISP) [DX0001]
PIC18LF45K80@QFN44 [DX4019]
PIC18LF45K80@QFN44(ISP) [DX0001]
PIC18LF45K80@TQFP44 [DX3003]
PIC18LF45K80@TQFP44(ISP) [DX0001]
PIC18LF4610 [DX0001]
PIC18LF4610(ISP)(Low-V) [DX0001]
PIC18LF4610@QFN44 [DX4018]
PIC18LF4610@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4610@QFN44(ML) [DX4019]
PIC18LF4610@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4610@TQFP44 [DX3003]
PIC18LF4610@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4620 [DX0001]
PIC18LF4620(ISP)(Low-V) [DX0001]
PIC18LF4620@QFN44 [DX4018]

PIC18LF4620@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4620@QFN44(ML) [DX4019]
PIC18LF4620@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4620@TQFP44 [DX3003]
PIC18LF4620@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4680 [DX0001]
PIC18LF4680(ISP)(High-V) [DX0001]
PIC18LF4680(ISP)(Low-V) [DX0001] PIC18LF4680@QFN44 [DX4018]
PIC18LF4680@QFN44(ISP)(High-V) [DX0001]
PIC18LF4680@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4680@QFN44(ML) [DX4019]
PIC18LF4680@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4680@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4680@TQFP44 [DX3003]
PIC18LF4680@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4680@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4682 [DX0001]
PIC18LF4682(ISP)(High-V) [DX0001]
PIC18LF4682(ISP)(Low-V) [DX0001] PIC18LF4682@QFN44 [DX4018]
PIC18LF4682@QFN44(ISP)(High-V) [DX0001]
PIC18LF4682@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4682@QFN44(ML) [DX4019]
PIC18LF4682@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4682@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4682@TQFP44 [DX3003]
PIC18LF4682@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4682@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF4685 [DX0001]
PIC18LF4685(ISP)(High-V) [DX0001]
PIC18LF4685(ISP)(Low-V) [DX0001] PIC18LF4685@QFN44 [DX4018]
PIC18LF4685@QFN44(ISP)(High-V) [DX0001]
PIC18LF4685@QFN44(ISP)(Low-V) [DX0001]
PIC18LF4685@QFN44(ML) [DX4019]
PIC18LF4685@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF4685@QFN44(ML)(ISP)(L-V) [DX0001]
PIC18LF4685@TQFP44 [DX3003]
PIC18LF4685@TQFP44(ISP)(High-V) [DX0001]
PIC18LF4685@TQFP44(ISP)(Low-V) [DX0001]
PIC18LF46J11 [DX0001] PIC18LF46J11(ISP) [DX0001]
PIC18LF46J11@QFN44 [DX4018] PIC18LF46J11@QFN44(ISP) [DX0001]
PIC18LF46J11@QFN44(ML) [DX4019]
PIC18LF46J11@QFN44(ML)(ISP) [DX0001]
PIC18LF46J11@TQFP44 [DX3003]
PIC18LF46J11@TQFP44(ISP) [DX0001]
PIC18LF46J13 [DX0001] PIC18LF46J13(ISP) [DX0001]
PIC18LF46J13@QFN44 [DX4018] PIC18LF46J13@QFN44(ML) [DX4019]
PIC18LF46J13@TQFP44 [DX3003] PIC18LF46J13QFN44(ISP) [DX0001]
PIC18LF46J13QFN44(ML)(ISP) [DX0001]

PIC18LF46J13TQFP44(ISP) [DX0001]　　PIC18LF46J50 [DX0001]
PIC18LF46J50(ISP) [DX0001]　　PIC18LF46J50@QFN44 [DX4018]
PIC18LF46J50@QFN44(ISP) [DX0001]　　PIC18LF46J50@QFN44(ML) [DX4019]
PIC18LF46J50@QFN44(ML)(ISP) [DX0001]
PIC18LF46J50@TQFP44 [DX3003]
PIC18LF46J50@TQFP44(ISP) [DX0001]
PIC18LF46J53 [DX0001]　　PIC18LF46J53(ISP) [DX0001]
PIC18LF46J53@QFN44 [DX4018]　　PIC18LF46J53@QFN44(ML) [DX4019]
PIC18LF46J53@TQFP44 [DX3003]　　PIC18LF46J53QFN44(ISP) [DX0001]
PIC18LF46J53QFN44(ML)(ISP) [DX0001]
PIC18LF46J53TQFP44(ISP) [DX0001]　　PIC18LF46K22 [DX0001]
PIC18LF46K22(ISP)(H-V) [DX0001]　　PIC18LF46K22@QFN44 [DX4018]
PIC18LF46K22@QFN44(ISP)(H-V) [DX0001]
PIC18LF46K22@QFN44(ML) [DX4019]
PIC18LF46K22@QFN44(ML)(ISP)(H-V) [DX0001]
PIC18LF46K22@TQFP44 [DX3003]
PIC18LF46K22@TQFP44(ISP)(H-V) [DX0001]
PIC18LF46K22@UQFN40 [DX4039]　　PIC18LF46K50 [DX0001]
PIC18LF46K50@ISP [DX0001]　　PIC18LF46K50@QFN44 [DX4019]
PIC18LF46K50@TQFP44 [DX3003]　　PIC18LF46K50@UQFN40 [DX4039]
PIC18LF46K80 [DX0001]　　PIC18LF46K80(ISP) [DX0001]
PIC18LF46K80@QFN44 [DX4019]　　PIC18LF46K80@QFN44(ISP) [DX0001]
PIC18LF46K80@TQFP44 [DX3003]
PIC18LF46K80@TQFP44(ISP) [DX0001]
PIC18LF47J13 [DX0001]　　PIC18LF47J13(ISP) [DX0001]
PIC18LF47J13@QFN44 [DX4018]　　PIC18LF47J13@QFN44(ML) [DX4019]
PIC18LF47J13@TQFP44 [DX3003]　　PIC18LF47J13QFN44(ISP) [DX0001]
PIC18LF47J13QFN44(ML)(ISP) [DX0001]
PIC18LF47J13TQFP44(ISP) [DX0001]　　PIC18LF47J53 [DX0001]
PIC18LF47J53(ISP) [DX0001]　　PIC18LF47J53@QFN44 [DX4018]
PIC18LF47J53@QFN44(ML) [DX4019]　　PIC18LF47J53@TQFP44 [DX3003]
PIC18LF47J53QFN44(ISP) [DX0001]
PIC18LF47J53QFN44(ML)(ISP) [DX0001]
PIC18LF47J53TQFP44(ISP) [DX0001]　　PIC18LF6310@TQFP64 [DX3011]
PIC18LF6310@TQFP64(ISP) [DX0001]　　PIC18LF6390@TQFP64 [DX3011]
PIC18LF6390@TQFP64(ISP) [DX0001]　　PIC18LF6393@TQFP64 [DX3011]
PIC18LF6393@TQFP64(ISP) [DX0001]　　PIC18LF63J11@TQFP64 [DX3011]
PIC18LF63J11@TQFP64(ISP) [DX0001]
PIC18LF63J90@TQFP64 [DX3011]
PIC18LF63J90@TQFP64(ISP) [DX0001]
PIC18LF6410@TQFP64 [DX3011]　　PIC18LF6410@TQFP64(ISP) [DX0001]
PIC18LF6490@TQFP64 [DX3011]　　PIC18LF6490@TQFP64(ISP) [DX0001]
PIC18LF6493@TQFP64 [DX3011]　　PIC18LF6493@TQFP64(ISP) [DX0001]
PIC18LF64J11@TQFP64 [DX3011]
PIC18LF64J11@TQFP64(ISP) [DX0001]
PIC18LF64J90@TQFP64 [DX3011]
PIC18LF64J90@TQFP64(ISP) [DX0001]
PIC18LF6520@TQFP64 [DX3011]　　PIC18LF6520@TQFP64(ISP) [DX0001]

PIC18LF6525@TQFP64 [DX3011]　　PIC18LF6525@TQFP64(ISP) [DX0001]
PIC18LF6527@TQFP64 [DX3011]
PIC18LF6527@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6527@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF6585@PLCC68 [DX2068]　　PIC18LF6585@PLCC68(ISP) [DX0001]
PIC18LF6585@TQFP64 [DX3011]　　PIC18LF6585@TQFP64(ISP) [DX0001]
PIC18LF65J11@TQFP64 [DX3011]
PIC18LF65J11@TQFP64(ISP) [DX0001]
PIC18LF65J90@TQFP64 [DX3011]
PIC18LF65J90@TQFP64(ISP) [DX0001]
PIC18LF65K80@QFN64 [DX4023]　　PIC18LF65K80@QFN64(ISP) [DX0001]
PIC18LF65K80@TQFP64 [DX3011]
PIC18LF65K80@TQFP64(ISP) [DX0001]
PIC18LF6620@TQFP64 [DX3011]　　PIC18LF6620@TQFP64(ISP) [DX0001]
PIC18LF6621@TQFP64 [DX3011]　　PIC18LF6621@TQFP64(ISP) [DX0001]
PIC18LF6622@TQFP64 [DX3011]
PIC18LF6622@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6622@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF6627@TQFP64 [DX3011]
PIC18LF6627@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6627@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF6628@TQFP64 [DX3011]
PIC18LF6628@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6628@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF6680@PLCC68 [DX2068]　　PIC18LF6680@PLCC68(ISP) [DX0001]
PIC18LF6680@TQFP64 [DX3011]　　PIC18LF6680@TQFP64(ISP) [DX0001]
PIC18LF66K80@QFN64 [DX4023]　　PIC18LF66K80@QFN64(ISP) [DX0001]
PIC18LF66K80@TQFP64 [DX3011]
PIC18LF66K80@TQFP64(ISP) [DX0001]
PIC18LF6720@TQFP64 [DX3011]　　PIC18LF6720@TQFP64(ISP) [DX0001]
PIC18LF6722@TQFP64 [DX3011]
PIC18LF6722@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6722@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF6723@TQFP64 [DX3011]
PIC18LF6723@TQFP64(ISP)(High-V) [DX0001]
PIC18LF6723@TQFP64(ISP)(Low-V) [DX0001]
PIC18LF8310@TQFP80 [DX3016]　　PIC18LF8310@TQFP80(ISP) [DX0001]
PIC18LF8390@TQFP80 [DX3016]　　PIC18LF8390@TQFP80(ISP) [DX0001]
PIC18LF8393@TQFP80 [DX3016]　　PIC18LF8393@TQFP80(ISP) [DX0001]
PIC18LF83J11@TQFP80 [DX3060]
PIC18LF83J11@TQFP80(ISP) [DX0001]
PIC18LF83J90@TQFP80 [DX3060]
PIC18LF83J90@TQFP80(ISP) [DX0001]
PIC18LF8410@TQFP80 [DX3016]　　PIC18LF8410@TQFP80(ISP) [DX0001]
PIC18LF8490@TQFP80 [DX3016]　　PIC18LF8490@TQFP80(ISP) [DX0001]
PIC18LF8493@TQFP80 [DX3016]　　PIC18LF8493@TQFP80(ISP) [DX0001]
PIC18LF84J11@TQFP80 [DX3060]
PIC18LF84J11@TQFP80(ISP) [DX0001]

PIC18LF84J90@TQFP80 [DX3060]
PIC18LF84J90@TQFP80(ISP) [DX0001]
PIC18LF8520@TQFP80 [DX3016]
PIC18LF8520@TQFP80(ISP) [DX0001]
PIC18LF8525@TQFP80 [DX3016]
PIC18LF8525@TQFP80(ISP) [DX0001]
PIC18LF8527@TQFP80 [DX3016]
PIC18LF8527@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8527@TQFP80(ISP)(Low-V) [DX0001]
PIC18LF8585@TQFP80 [DX3016]
PIC18LF8585@TQFP80(ISP) [DX0001]
PIC18LF85J11@TQFP80 [DX3060]
PIC18LF85J11@TQFP80(ISP) [DX0001]
PIC18LF85J90@TQFP80 [DX3060]
PIC18LF85J90@TQFP80(ISP) [DX0001]
PIC18LF8620@TQFP80 [DX3016]
PIC18LF8620@TQFP80(ISP) [DX0001]
PIC18LF8621@TQFP80 [DX3016]
PIC18LF8621@TQFP80(ISP) [DX0001]
PIC18LF8622@TQFP80 [DX3016]
PIC18LF8622@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8622@TQFP80(ISP)(Low-V) [DX0001]
PIC18LF8627@TQFP80 [DX3016]
PIC18LF8627@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8627@TQFP80(ISP)(Low-V) [DX0001]
PIC18LF8628@TQFP80 [DX3016]
PIC18LF8628@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8628@TQFP80(ISP)(Low-V) [DX0001]
PIC18LF8680@TQFP80 [DX3016]
PIC18LF8680@TQFP80(ISP) [DX0001]
PIC18LF8720@TQFP80 [DX3016]
PIC18LF8720@TQFP80(ISP) [DX0001]
PIC18LF8722@TQFP80 [DX3016]
PIC18LF8722@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8722@TQFP80(ISP)(Low-V) [DX0001]
PIC18LF8723@TQFP80 [DX3016]
PIC18LF8723@TQFP80(ISP)(High-V) [DX0001]
PIC18LF8723@TQFP80(ISP)(Low-V) [DX0001]
PIC24EP128GP202 [DX0001]
PIC24EP128GP202(ISP) [DX0001]
PIC24EP128GP202@QFN28 [DX4014]
PIC24EP128GP202@SOIC28 [DX1033]
PIC24EP128GP202@SSOP28 [DX1026]
PIC24EP128GP203(ISP) [DX0001]
PIC24EP128GP203@VTLA36 [DX4077]
PIC24EP128GP204(ISP) [DX0001]
PIC24EP128GP204@QFN44 [DX4019]
PIC24EP128GP204@TQFP44 [DX3003#2]
PIC24EP128GP206(ISP) [DX0001]
PIC24EP128GP206@QFN64 [DX4023]
PIC24EP128GP206@TQFP64 [DX3011]
PIC24EP128MC202 [DX0001]
PIC24EP128MC202(ISP) [DX0001]
PIC24EP128MC202@QFN28 [DX4014]
PIC24EP128MC202@SOIC28 [DX1033]
PIC24EP128MC202@SSOP28 [DX1026]
PIC24EP128MC203(ISP) [DX0001]
PIC24EP128MC203@VTLA36 [DX4077]
PIC24EP128MC204(ISP) [DX0001]
PIC24EP128MC204@QFN44 [DX4019]
PIC24EP128MC204@TQFP44 [DX3003#2]
PIC24EP128MC204@VTLA44 [DX4079]
PIC24EP128MC206(ISP) [DX0001]
PIC24EP128MC206@QFN64 [DX4023]
PIC24EP128MC206@TQFP64 [DX3011]
PIC24EP256GP202 [DX0001]
PIC24EP256GP202(ISP) [DX0001]
PIC24EP256GP202@QFN28 [DX4014]
PIC24EP256GP202@SOIC28 [DX1033]

PIC24EP256GP202@SSOP28 [DX1026]
PIC24EP256GP203(ISP) [DX0001]
PIC24EP256GP203@VTLA36 [DX4077]
PIC24EP256GP204(ISP) [DX0001]
PIC24EP256GP204@QFN44 [DX4019]
PIC24EP256GP204@TQFP44 [DX3003#2]
PIC24EP256GP206(ISP) [DX0001]
PIC24EP256GP206@QFN64 [DX4023]
PIC24EP256GP206@TQFP64 [DX3011]
PIC24EP256MC202 [DX0001]
PIC24EP256MC202(ISP) [DX0001]
PIC24EP256MC202@QFN28 [DX4014]
PIC24EP256MC202@SOIC28 [DX1033]
PIC24EP256MC202@SSOP28 [DX1026]
PIC24EP256MC203(ISP) [DX0001]
PIC24EP256MC203@VTLA36 [DX4077]
PIC24EP256MC204(ISP) [DX0001]
PIC24EP256MC204@QFN44 [DX4019]
PIC24EP256MC204@TQFP44 [DX3003#2]
PIC24EP256MC204@VTLA44 [DX4079]
PIC24EP256MC206(ISP) [DX0001]
PIC24EP256MC206@QFN64 [DX4023]
PIC24EP256MC206@TQFP64 [DX3011]
PIC24EP32GP202 [DX0001]
PIC24EP32GP202(ISP) [DX0001]
PIC24EP32GP202@QFN28 [DX4014]
PIC24EP32GP202@SOIC28 [DX1033]
PIC24EP32GP202@SSOP28 [DX1026]
PIC24EP32GP203(ISP) [DX0001]
PIC24EP32GP203@VTLA36 [DX4077]
PIC24EP32GP204(ISP) [DX0001]
PIC24EP32GP204@QFN44 [DX4019]
PIC24EP32GP204@TQFP44 [DX3003]
PIC24EP32MC202 [DX0001]
PIC24EP32MC202(ISP) [DX0001]
PIC24EP32MC202@QFN28 [DX4014]
PIC24EP32MC202@SOIC28 [DX1033]
PIC24EP32MC202@SSOP28 [DX1026]
PIC24EP32MC203(ISP) [DX0001]
PIC24EP32MC203@VTLA36 [DX4077]
PIC24EP32MC204(ISP) [DX0001]
PIC24EP32MC204@QFN44 [DX4019]
PIC24EP32MC204@TQFP44 [DX3003]
PIC24EP32MC204@VTLA44 [DX4079]
PIC24EP512GP202 [DX0001]
PIC24EP512GP202(ISP) [DX0001]
PIC24EP512GP202@QFN28 [DX4014]
PIC24EP512GP202@SOIC28 [DX1033]
PIC24EP512GP204(ISP) [DX0001]
PIC24EP512GP204@QFN44 [DX4019]
PIC24EP512GP204@TQFP44 [DX3003#2]
PIC24EP512GP204@VTLA44 [DX4079]
PIC24EP512GP206(ISP) [DX0001]
PIC24EP512GP206@QFN64 [DX4023]
PIC24EP512GP206@TQFP64 [DX3011]
PIC24EP512MC202 [DX0001]
PIC24EP512MC202(ISP) [DX0001]
PIC24EP512MC202@QFN28 [DX4014]
PIC24EP512MC202@SOIC28 [DX1033]
PIC24EP512MC204(ISP) [DX0001]
PIC24EP512MC204@QFN44 [DX4019]
PIC24EP512MC204@TQFP44 [DX3003#2]
PIC24EP512MC204@VTLA44 [DX4079]
PIC24EP512MC206(ISP) [DX0001]
PIC24EP512MC206@QFN64 [DX4023]
PIC24EP512MC206@TQFP64 [DX3011]
PIC24EP64GP202 [DX0001]
PIC24EP64GP202(ISP) [DX0001]
PIC24EP64GP202@QFN28 [DX4014]
PIC24EP64GP202@SOIC28 [DX1033]
PIC24EP64GP202@SSOP28 [DX1026]
PIC24EP64GP203(ISP) [DX0001]
PIC24EP64GP203@VTLA36 [DX4077]
PIC24EP64GP204(ISP) [DX0001]
PIC24EP64GP204@QFN44 [DX4019]
PIC24EP64GP204@TQFP44 [DX3003]
PIC24EP64GP204@VTLA44 [DX4078]
PIC24EP64GP206(ISP) [DX0001]
PIC24EP64GP206@QFN64 [DX4023]
PIC24EP64GP206@TQFP64 [DX3011]
PIC24EP64MC202 [DX0001]
PIC24EP64MC202(ISP) [DX0001]
PIC24EP64MC202@QFN28 [DX4014]
PIC24EP64MC202@SOIC28 [DX1033]
PIC24EP64MC202@SSOP28 [DX1026]
PIC24EP64MC203(ISP) [DX0001]
PIC24EP64MC203@VTLA36 [DX4077]
PIC24EP64MC204(ISP) [DX0001]
PIC24EP64MC204@QFN44 [DX4019]
PIC24EP64MC204@TQFP44 [DX3003]

PIC24EP64MC204@VTLA44 [DX4078]
PIC24EP64MC206(ISP) [DX0001]
PIC24EP64MC206@QFN64 [DX4023]
PIC24EP64MC206@TQFP64 [DX3011]
PIC24F04KA200 [DX0001]
PIC24F04KA200(ISP) [DX0001]
PIC24F04KA200@SOIC14 [DX1033]
PIC24F04KA201 [DX0001]
PIC24F04KA201(ISP) [DX0001]
PIC24F04KA201@QFN20 [DX4025]
PIC24F04KA201@SOIC20 [DX1033]
PIC24F04KA201@SSOP20 [DX1026]
PIC24F04KL100 [DX0001]
PIC24F04KL100(ISP) [DX0001]
PIC24F04KL100@SOIC14 [DX1033]
PIC24F04KL101 [DX0001]
PIC24F04KL101(ISP) [DX0001]
PIC24F04KL101@QFN20 [DX4025]
PIC24F04KL101@SOIC20 [DX1033]
PIC24F04KL101@SSOP20 [DX1026]
PIC24F08KA101 [DX0001]
PIC24F08KA101(ISP) [DX0001]
PIC24F08KA101@QFN20 [DX4025]
PIC24F08KA101@SOIC20 [DX1033]
PIC24F08KA101@SSOP20 [DX1026]
PIC24F08KA102 [DX0001]
PIC24F08KA102(ISP) [DX0001]
PIC24F08KA102@QFN28 [DX4014]
PIC24F08KA102@SOIC28 [DX1033]
PIC24F08KA102@SSOP28 [DX1026]
PIC24F08KL200 [DX0001]
PIC24F08KL200(ISP) [DX0001]
PIC24F08KL200@SOIC14 [DX1033]
PIC24F08KL201 [DX0001]
PIC24F08KL201(ISP) [DX0001]
PIC24F08KL201@QFN20 [DX4025]
PIC24F08KL201@SOIC20 [DX1033]
PIC24F08KL201@SSOP20 [DX1026]
PIC24F08KL301 [DX0001]
PIC24F08KL301(ISP) [DX0001]
PIC24F08KL301@QFN20 [DX4025]
PIC24F08KL301@SOIC20 [DX1033]
PIC24F08KL301@SSOP20 [DX1026]
PIC24F08KL302 [DX0001]
PIC24F08KL302(ISP) [DX0001]
PIC24F08KL302(ML)@QFN28 [DX4014]
PIC24F08KL302@QFN28 [DX4013]
PIC24F08KL302@SOIC28 [DX1033]
PIC24F08KL302@SSOP28 [DX1026]
PIC24F08KL401 [DX0001]
PIC24F08KL401(ISP) [DX0001]
PIC24F08KL401@QFN20 [DX4025]
PIC24F08KL401@SOIC20 [DX1033]
PIC24F08KL401@SSOP20 [DX1026]
PIC24F08KL402 [DX0001]
PIC24F08KL402(ISP) [DX0001]
PIC24F08KL402(ML)@QFN28 [DX4014]
PIC24F08KL402@QFN28 [DX4013]
PIC24F08KL402@SOIC28 [DX1033]
PIC24F08KL402@SSOP28 [DX1026]
PIC24F16KA101 [DX0001]
PIC24F16KA101(ISP) [DX0001]
PIC24F16KA101@QFN20 [DX4025]
PIC24F16KA101@SOIC20 [DX1033]
PIC24F16KA101@SSOP20 [DX1026]
PIC24F16KA102 [DX0001]
PIC24F16KA102(ISP) [DX0001]
PIC24F16KA102@QFN28 [DX4014]
PIC24F16KA102@SOIC28 [DX1033]
PIC24F16KA102@SSOP28 [DX1026]
PIC24F16KA301 [DX0001]
PIC24F16KA301(ISP) [DX0001]
PIC24F16KA301@QFN20 [DX4025]
PIC24F16KA301@SOIC20 [DX1033]
PIC24F16KA301@SSOP20 [DX1026]
PIC24F16KA302 [DX0001]
PIC24F16KA302(ISP) [DX0001]
PIC24F16KA302@QFN28 [DX4014]
PIC24F16KA302@SOIC28 [DX1033]
PIC24F16KA302@SSOP28 [DX1026]
PIC24F16KA304(ISP) [DX0001]
PIC24F16KA304@QFN44 [DX4019]
PIC24F16KA304@TQFP44 [DX3003]
PIC24F16KA304@UQFN48 [DX4043]
PIC24F16KL401 [DX0001]
PIC24F16KL401(ISP) [DX0001]
PIC24F16KL401@QFN20 [DX4025]
PIC24F16KL401@SOIC20 [DX1033]
PIC24F16KL401@SSOP20 [DX1026]
PIC24F16KL402 [DX0001]
PIC24F16KL402(ISP) [DX0001]
PIC24F16KL402(ML)@QFN28 [DX4014]
PIC24F16KL402@QFN28 [DX4013]
PIC24F16KL402@SOIC28 [DX1033]
PIC24F16KL402@SSOP28 [DX1026]
PIC24F32KA301 [DX0001]

PIC24F32KA301(ISP) [DX0001]
PIC24F32KA301@QFN20 [DX4025]
PIC24F32KA301@SOIC20 [DX1033]
PIC24F32KA301@SSOP20 [DX1026]
PIC24F32KA302 [DX0001]
PIC24F32KA302(ISP) [DX0001]
PIC24F32KA302@QFN28 [DX4014]
PIC24F32KA302@SOIC28 [DX1033]
PIC24F32KA302@SSOP28 [DX1026]
PIC24F32KA304(ISP) [DX0001]
PIC24F32KA304@QFN44 [DX4019]
PIC24F32KA304@TQFP44 [DX3003]
PIC24F32KA304@UQFN48 [DX4043]
PIC24FJ128DA106(ISP) [DX0001]
PIC24FJ128DA106@QFN64 [DX4023]
PIC24FJ128DA106@TQFP64 [DX3011]
PIC24FJ128DA110(ISP) [DX0001]
PIC24FJ128DA110@TQFP100(1) [DX3021]
PIC24FJ128DA110@TQFP100(2) [DX3071]
PIC24FJ128DA110@XBGA121 [DX5058]
PIC24FJ128DA206(ISP) [DX0001]
PIC24FJ128DA206@QFN64 [DX4023]
PIC24FJ128DA206@TQFP64 [DX3011]
PIC24FJ128DA210(ISP) [DX0001]
PIC24FJ128DA210@TQFP100(1) [DX3021]
PIC24FJ128DA210@TQFP100(2) [DX3071]
PIC24FJ128DA210@XBGA121 [DX5058]
PIC24FJ128GA006@QFN64 [DX4023]
PIC24FJ128GA006@QFN64(ISP) [DX0001]
PIC24FJ128GA006@TQFP64 [DX3011]
PIC24FJ128GA006@TQFP64(ISP) [DX0001]
PIC24FJ128GA008@TQFP80 [DX3016]
PIC24FJ128GA008@TQFP80(ISP) [DX0001]
PIC24FJ128GA010@QFP100 [DX3021]
PIC24FJ128GA010@QFP100(ISP) [DX0001]
PIC24FJ128GA010@TQFP100 [DX3071]
PIC24FJ128GA010@TQFP100(ISP) [DX0001]
PIC24FJ128GA106@QFN64 [DX4023]
PIC24FJ128GA106@QFN64(ISP) [DX0001]
PIC24FJ128GA106@TQFP64 [DX3011]
PIC24FJ128GA106@TQFP64(ISP) [DX0001]
PIC24FJ128GA108@TQFP80 [DX3016]
PIC24FJ128GA108@TQFP80(ISP) [DX0001]
PIC24FJ128GA110@TQFP100(12*12*1) [DX3071]
PIC24FJ128GA110@TQFP100(14*14*1) [DX3021]
PIC24FJ128GA110@TQFP100-1(ISP) [DX0001]
PIC24FJ128GA110@TQFP100-2(ISP) [DX0001]
PIC24FJ128GA306(ISP) [DX0001]
PIC24FJ128GA306@QFN64 [DX4023]
PIC24FJ128GA306@TQFP64 [DX3011]
PIC24FJ128GA308(ISP) [DX0001]
PIC24FJ128GA308@TQFP80 [DX3016]
PIC24FJ128GA310(ISP) [DX0001]
PIC24FJ128GA310@TQFP100(1) [DX3021]
PIC24FJ128GA310@TQFP100(2) [DX3071]
PIC24FJ128GA310@XBGA121 [DX5058]
PIC24FJ128GB106@QFN64 [DX4023]
PIC24FJ128GB106@QFN64(ISP) [DX0001]
PIC24FJ128GB106@TQFP64 [DX3011]
PIC24FJ128GB106@TQFP64(ISP) [DX0001]
PIC24FJ128GB108@TQFP80 [DX3016]
PIC24FJ128GB108@TQFP80(ISP) [DX0001]
PIC24FJ128GB110@TQFP100(12*12*1) [DX3071]

PIC24FJ128GB110@TQFP100(14*14*1) [DX3021]
PIC24FJ128GB110@TQFP100-1(ISP) [DX0001]
PIC24FJ128GB110@TQFP100-2(ISP) [DX0001]
PIC24FJ128GB206(ISP) [DX0001]
PIC24FJ128GB206@QFN64 [DX4023]
PIC24FJ128GB206@TQFP64 [DX3011]
PIC24FJ128GB210(ISP) [DX0001]
PIC24FJ128GB210@TQFP100(1) [DX3021]
PIC24FJ128GB210@TQFP100(2) [DX3071]
PIC24FJ128GB210@XBGA121 [DX5058]
PIC24FJ128GC006(ISP) [DX0001]
PIC24FJ128GC006@QFN64 [DX4023]
PIC24FJ128GC006@TQFP64 [DX3011]
PIC24FJ128GC008(ISP) [DX0001]
PIC24FJ128GC008@TQFP80 [DX3016]
PIC24FJ128GC010(ISP) [DX0001]
PIC24FJ128GC010@TQFP100(1) [DX3021]
PIC24FJ128GC010@TQFP100(2) [DX3071]
PIC24FJ128GC010@XBGA121 [DX5058]
PIC24FJ16GA002 [DX0001]
PIC24FJ16GA002(ISP) [DX0001]
PIC24FJ16GA002@QFN28 [DX4014]
PIC24FJ16GA002@QFN28(ISP) [DX0001]
PIC24FJ16GA002@SOIC28 [DX1033]
PIC24FJ16GA002@SOIC28(ISP) [DX0001]
PIC24FJ16GA002@SSOP28 [DX1026]
PIC24FJ16GA002@SSOP28(ISP) [DX0001]
PIC24FJ16GA004@QFN44 [DX4019]
PIC24FJ16GA004@QFN44(ISP) [DX0001]
PIC24FJ16GA004@TQFP44 [DX3003]
PIC24FJ16GA004@TQFP44(ISP) [DX0001]
PIC24FJ192GA106@QFN64 [DX4023]
PIC24FJ192GA106@QFN64(ISP) [DX0001]
PIC24FJ192GA106@TQFP64 [DX3011]
PIC24FJ192GA106@TQFP64(ISP) [DX0001]
PIC24FJ192GA108@TQFP80 [DX3016]
PIC24FJ192GA108@TQFP80(ISP) [DX0001]
PIC24FJ192GA110@TQFP100(12*12*1) [DX3071]
PIC24FJ192GA110@TQFP100(14*14*1) [DX3021]
PIC24FJ192GA110@TQFP100-1(ISP) [DX0001]
PIC24FJ192GA110@TQFP100-2(ISP) [DX0001]
PIC24FJ192GB106@QFN64 [DX4023]
PIC24FJ192GB106@QFN64(ISP) [DX0001]
PIC24FJ192GB106@TQFP64 [DX3011]
PIC24FJ192GB106@TQFP64(ISP) [DX0001]
PIC24FJ192GB108@TQFP80 [DX3016]
PIC24FJ192GB108@TQFP80(ISP) [DX0001]
PIC24FJ192GB110@TQFP100(12*12*1) [DX3071]
PIC24FJ192GB110@TQFP100(14*14*1) [DX3021]
PIC24FJ192GB110@TQFP100-1(ISP) [DX0001]
PIC24FJ192GB110@TQFP100-2(ISP) [DX0001]
PIC24FJ256DA106(ISP) [DX0001]
PIC24FJ256DA106@QFN64 [DX4023]
PIC24FJ256DA106@TQFP64 [DX3011]
PIC24FJ256DA110(ISP) [DX0001]
PIC24FJ256DA110@TQFP100(1) [DX3021]
PIC24FJ256DA110@TQFP100(2) [DX3071]

PIC24FJ256DA110@XBGA121 [DX5058]　　PIC24FJ256DA206(ISP) [DX0001]
PIC24FJ256DA206@QFN64 [DX4023]　　PIC24FJ256DA206@TQFP64 [DX3011]
PIC24FJ256DA210(ISP) [DX0001]
PIC24FJ256DA210@TQFP100(1) [DX3021]
PIC24FJ256DA210@TQFP100(2) [DX3071]
PIC24FJ256DA210@XBGA121 [DX5058]　　PIC24FJ256GA106@QFN64 [DX4023]
PIC24FJ256GA106@QFN64(ISP) [DX0001]
PIC24FJ256GA106@TQFP64 [DX3011]
PIC24FJ256GA106@TQFP64(ISP) [DX0001]
PIC24FJ256GA108@TQFP80 [DX3016]
PIC24FJ256GA108@TQFP80(ISP) [DX0001]
PIC24FJ256GA110@TQFP100(12*12*1) [DX3071]
PIC24FJ256GA110@TQFP100(14*14*1) [DX3021]
PIC24FJ256GA110@TQFP100-1(ISP) [DX0001]
PIC24FJ256GA110@TQFP100-2(ISP) [DX0001]
PIC24FJ256GB106@QFN64 [DX4023]
PIC24FJ256GB106@QFN64(ISP) [DX0001]
PIC24FJ256GB106@TQFP64 [DX3011]
PIC24FJ256GB106@TQFP64(ISP) [DX0001]
PIC24FJ256GB108@TQFP80 [DX3016]
PIC24FJ256GB108@TQFP80(ISP) [DX0001]
PIC24FJ256GB110@TQFP100(12*12*1) [DX3071]
PIC24FJ256GB110@TQFP100(14*14*1) [DX3021]
PIC24FJ256GB110@TQFP100-1(ISP) [DX0001]
PIC24FJ256GB110@TQFP100-2(ISP) [DX0001]
PIC24FJ256GB206(ISP) [DX0001]　　PIC24FJ256GB206@QFN64 [DX4023]
PIC24FJ256GB206@TQFP64 [DX3011]　　PIC24FJ256GB210(ISP) [DX0001]
PIC24FJ256GB210@TQFP100(1) [DX3021]
PIC24FJ256GB210@TQFP100(2) [DX3071]
PIC24FJ256GB210@XBGA121 [DX5058]　　PIC24FJ32GA002 [DX0001]
PIC24FJ32GA002(ISP) [DX0001]　　PIC24FJ32GA002@QFN28 [DX4014]
PIC24FJ32GA002@QFN28(ISP) [DX0001]
PIC24FJ32GA002@SOIC28 [DX1033]
PIC24FJ32GA002@SOIC28(ISP) [DX0001]
PIC24FJ32GA002@SSOP28 [DX1026]
PIC24FJ32GA002@SSOP28(ISP) [DX0001]
PIC24FJ32GA004@QFN44 [DX4019]
PIC24FJ32GA004@QFN44(ISP) [DX0001]
PIC24FJ32GA004@TQFP44 [DX3003]
PIC24FJ32GA004@TQFP44(ISP) [DX0001]
PIC24FJ32GA102 [DX0001]　　PIC24FJ32GA102(ISP) [DX0001]
PIC24FJ32GA102@QFN28 [DX4014]
PIC24FJ32GA102@QFN28(ISP) [DX0001]
PIC24FJ32GA102@SOIC28 [DX1033]
PIC24FJ32GA102@SOIC28(ISP) [DX0001]
PIC24FJ32GA104@QFN44 [DX4019]
PIC24FJ32GA104@QFN44(ISP) [DX0001]
PIC24FJ32GA104@TQFP44 [DX3003]

PIC24FJ32GA104@TQFP44(ISP) [DX0001]
PIC24FJ32GB002 [DX0001]
PIC24FJ32GB002(ISP) [DX0001]
PIC24FJ32GB002@QFN28 [DX4014]
PIC24FJ32GB002@QFN28(ISP) [DX0001]
PIC24FJ32GB002@SOIC28 [DX1033]
PIC24FJ32GB002@SOIC28(ISP) [DX0001]
PIC24FJ32GB004@QFN44 [DX4019]
PIC24FJ32GB004@QFN44(ISP) [DX0001]
PIC24FJ32GB004@TQFP44 [DX3003]
PIC24FJ32GB004@TQFP44(ISP) [DX0001]
PIC24FJ48GA002 [DX0001]
PIC24FJ48GA002(ISP) [DX0001]
PIC24FJ48GA002@QFN28 [DX4014]
PIC24FJ48GA002@QFN28(ISP) [DX0001]
PIC24FJ48GA002@SOIC28 [DX1033]
PIC24FJ48GA002@SOIC28(ISP) [DX0001]
PIC24FJ48GA002@SSOP28 [DX1026]
PIC24FJ48GA002@SSOP28(ISP) [DX0001]
PIC24FJ48GA004@QFN44 [DX4019]
PIC24FJ48GA004@QFN44(ISP) [DX0001]
PIC24FJ48GA004@TQFP44 [DX3003]
PIC24FJ48GA004@TQFP44(ISP) [DX0001]
PIC24FJ64GA002 [DX0001]
PIC24FJ64GA002(ISP) [DX0001]
PIC24FJ64GA002@QFN28 [DX4014]
PIC24FJ64GA002@QFN28(ISP) [DX0001]
PIC24FJ64GA002@SOIC28 [DX1033]
PIC24FJ64GA002@SOIC28(ISP) [DX0001]
PIC24FJ64GA002@SSOP28 [DX1026]
PIC24FJ64GA002@SSOP28(ISP) [DX0001]
PIC24FJ64GA004@QFN44 [DX4019]
PIC24FJ64GA004@QFN44(ISP) [DX0001]
PIC24FJ64GA004@TQFP44 [DX3003]
PIC24FJ64GA004@TQFP44(ISP) [DX0001]
PIC24FJ64GA006@QFN64 [DX4023]
PIC24FJ64GA006@QFN64(ISP) [DX0001]
PIC24FJ64GA006@TQFP64 [DX3011]
PIC24FJ64GA006@TQFP64(ISP) [DX0001]
PIC24FJ64GA008@TQFP80 [DX3016]
PIC24FJ64GA008@TQFP80(ISP) [DX0001]
PIC24FJ64GA010@QFP100 [DX3021]
PIC24FJ64GA010@QFP100(ISP) [DX0001]
PIC24FJ64GA010@TQFP100 [DX3071]
PIC24FJ64GA010@TQFP100(ISP) [DX0001]
PIC24FJ64GA102 [DX0001]
PIC24FJ64GA102(ISP) [DX0001]
PIC24FJ64GA102@QFN28 [DX4014]
PIC24FJ64GA102@QFN28(ISP) [DX0001]
PIC24FJ64GA102@SOIC28 [DX1033]
PIC24FJ64GA102@SOIC28(ISP) [DX0001]
PIC24FJ64GA104@QFN44 [DX4019]

PIC24FJ64GA104@QFN44(ISP) [DX0001]
PIC24FJ64GA104@TQFP44 [DX3003]
PIC24FJ64GA104@TQFP44(ISP) [DX0001]
PIC24FJ64GA106@QFN64 [DX4023]
PIC24FJ64GA106@QFN64(ISP) [DX0001]
PIC24FJ64GA106@TQFP64 [DX3011]
PIC24FJ64GA106@TQFP64(ISP) [DX0001]
PIC24FJ64GA108@TQFP80 [DX3016]
PIC24FJ64GA108@TQFP80(ISP) [DX0001]
PIC24FJ64GA110@TQFP100(12*12*1) [DX3071]
PIC24FJ64GA110@TQFP100(14*14*1) [DX3021]
PIC24FJ64GA110@TQFP100-1(ISP) [DX0001]
PIC24FJ64GA110@TQFP100-2(ISP) [DX0001]
PIC24FJ64GA306(ISP) [DX0001]
PIC24FJ64GA306@QFN64 [DX4023]
PIC24FJ64GA306@TQFP64 [DX3011]
PIC24FJ64GA308(ISP) [DX0001]
PIC24FJ64GA308@TQFP80 [DX3016]
PIC24FJ64GA310(ISP) [DX0001]
PIC24FJ64GA310@TQFP100(1) [DX3021]
PIC24FJ64GA310@TQFP100(2) [DX3071]
PIC24FJ64GA310@XBGA121 [DX5058]
PIC24FJ64GB002 [DX0001]
PIC24FJ64GB002(ISP) [DX0001]
PIC24FJ64GB002@QFN28 [DX4014]
PIC24FJ64GB002@QFN28(ISP) [DX0001]
PIC24FJ64GB002@SOIC28 [DX1033]
PIC24FJ64GB002@SOIC28(ISP) [DX0001]
PIC24FJ64GB004@QFN44 [DX4019]
PIC24FJ64GB004@QFN44(ISP) [DX0001]
PIC24FJ64GB004@TQFP44 [DX3003]
PIC24FJ64GB004@TQFP44(ISP) [DX0001]
PIC24FJ64GB106@QFN64 [DX4023]
PIC24FJ64GB106@QFN64(ISP) [DX0001]
PIC24FJ64GB106@TQFP64 [DX3011]
PIC24FJ64GB106@TQFP64(ISP) [DX0001]
PIC24FJ64GB108@TQFP80 [DX3016]
PIC24FJ64GB108@TQFP80(ISP) [DX0001]
PIC24FJ64GB110@TQFP100(12*12*1) [DX3071]
PIC24FJ64GB110@TQFP100(14*14*1) [DX3021]
PIC24FJ64GB110@TQFP100-1(ISP) [DX0001]
PIC24FJ64GB110@TQFP100-2(ISP) [DX0001]
PIC24FJ64GC006(ISP) [DX0001]
PIC24FJ64GC006@QFN64 [DX4023]
PIC24FJ64GC006@TQFP64 [DX3011]
PIC24FJ64GC008(ISP) [DX0001]
PIC24FJ64GC008@TQFP80 [DX3016]
PIC24FJ64GC010(ISP) [DX0001]
PIC24FJ64GC010@TQFP100(1) [DX3021]
PIC24FJ64GC010@TQFP100(2) [DX3071]
PIC24FJ64GC010@XBGA121 [DX5058]
PIC24FJ96GA006@QFN64 [DX4023]
PIC24FJ96GA006@QFN64(ISP) [DX0001]
PIC24FJ96GA006@TQFP64 [DX3011]
PIC24FJ96GA006@TQFP64(ISP) [DX0001]
PIC24FJ96GA008@TQFP80 [DX3016]
PIC24FJ96GA008@TQFP80(ISP) [DX0001]

PIC24FJ96GA010@QFP100 [DX3021]
PIC24FJ96GA010@QFP100(ISP) [DX0001]
PIC24FJ96GA010@TQFP100 [DX3071]
PIC24FJ96GA010@TQFP100(ISP) [DX0001]
PIC24FV08KM101 [DX0001]
PIC24FV08KM101(ISP) [DX0001]
PIC24FV08KM101@QFN28 [DX4025]
PIC24FV08KM101@SOIC28 [DX1033]
PIC24FV08KM101@SSOP28 [DX1026]
PIC24FV08KM102 [DX0001]
PIC24FV08KM102(ISP) [DX0001]
PIC24FV08KM102(ML)@QFN28 [DX4014]
PIC24FV08KM102@QFN28 [DX4013]
PIC24FV08KM102@SOIC28 [DX1033]
PIC24FV08KM102@SSOP28 [DX1026]
PIC24FV08KM202 [DX0001]
PIC24FV08KM202(ISP) [DX0001]
PIC24FV08KM202(ML)@QFN28 [DX4014]
PIC24FV08KM202@QFN28 [DX4013]
PIC24FV08KM202@SOIC28 [DX1033]
PIC24FV08KM202@SSOP28 [DX1026]
PIC24FV08KM204(ISP) [DX0001]
PIC24FV08KM204@QFN44 [DX4019]
PIC24FV08KM204@QFN48 [DX4043]
PIC24FV08KM204@TQFP44 [DX3003]
PIC24FV16KA301 [DX0001]
PIC24FV16KA301(ISP) [DX0001]
PIC24FV16KA301@QFN20 [DX4025]
PIC24FV16KA301@SOIC20 [DX1033]
PIC24FV16KA301@SSOP20 [DX1026]
PIC24FV16KA302 [DX0001]
PIC24FV16KA302(ISP) [DX0001]
PIC24FV16KA302@QFN28 [DX4014]
PIC24FV16KA302@QFN44 [DX4019]
PIC24FV16KA302@SOIC28 [DX1033]
PIC24FV16KA302@SSOP28 [DX1026]
PIC24FV16KA302@TQFP44 [DX3003]
PIC24FV16KA302@UQFN48 [DX4043]
PIC24FV16KA304(ISP) [DX0001]
PIC24FV16KM102 [DX0001]
PIC24FV16KM102(ISP) [DX0001]
PIC24FV16KM102(ML)@QFN28 [DX4014]
PIC24FV16KM102@QFN28 [DX4013]
PIC24FV16KM102@SOIC28 [DX1033]
PIC24FV16KM102@SSOP28 [DX1026]
PIC24FV16KM104(ISP) [DX0001]
PIC24FV16KM104@QFN44 [DX4019]
PIC24FV16KM104@QFN48 [DX4043]
PIC24FV16KM104@TQFP44 [DX3003]
PIC24FV16KM202 [DX0001]
PIC24FV16KM202(ISP) [DX0001]
PIC24FV16KM202(ML)@QFN28 [DX4014]
PIC24FV16KM202@QFN28 [DX4013]
PIC24FV16KM202@SOIC28 [DX1033]
PIC24FV16KM202@SSOP28 [DX1026]
PIC24FV16KM204(ISP) [DX0001]
PIC24FV16KM204@QFN44 [DX4019]
PIC24FV16KM204@QFN48 [DX4043]
PIC24FV16KM204@TQFP44 [DX3003]
PIC24FV32KA301 [DX0001]
PIC24FV32KA301(ISP) [DX0001]
PIC24FV32KA301@QFN20 [DX4025]
PIC24FV32KA301@SOIC20 [DX1033]
PIC24FV32KA301@SSOP20 [DX1026]
PIC24FV32KA302 [DX0001]
PIC24FV32KA302(ISP) [DX0001]
PIC24FV32KA302@QFN28 [DX4014]
PIC24FV32KA302@QFN44 [DX4019]
PIC24FV32KA302@SOIC28 [DX1033]
PIC24FV32KA302@SSOP28 [DX1026]
PIC24FV32KA302@TQFP44 [DX3003]
PIC24FV32KA302@UQFN44 [DX4043]
PIC24FV32KA304(ISP) [DX0001]
PIC24HJ128GP202 [DX0001]
PIC24HJ128GP202(ISP) [DX0001]
PIC24HJ128GP202@QFN28 [DX4032]
PIC24HJ128GP202@SOIC28 [DX1033]
PIC24HJ128GP202@SSOP28 [DX1026]
PIC24HJ128GP204(ISP) [DX0001]
PIC24HJ128GP204@QFN44 [DX4019]
PIC24HJ128GP204@TQFP44 [DX3003]
PIC24HJ128GP206(ISP) [DX0001]
PIC24HJ128GP206@QFN64 [DX4023]
PIC24HJ128GP206@TQFP64 [DX3011]

PIC24HJ128GP206A(ISP) [DX0001]　　PIC24HJ128GP206A@QFN64 [DX4023]
PIC24HJ128GP206A@TQFP64 [DX3011]　　PIC24HJ128GP210(ISP) [DX0001]
PIC24HJ128GP210@TQFP100(1) [DX3021]
PIC24HJ128GP210@TQFP100(2) [DX3071]
PIC24HJ128GP210A(ISP) [DX0001]
PIC24HJ128GP210A@TQFP100(1) [DX3021]
PIC24HJ128GP210A@TQFP100(2) [DX3071]
PIC24HJ128GP306(ISP) [DX0001]　　PIC24HJ128GP306@QFN64 [DX4023]
PIC24HJ128GP306@TQFP64 [DX3011]　　PIC24HJ128GP306A(ISP) [DX0001]
PIC24HJ128GP306A@QFN64 [DX4023]　　PIC24HJ128GP306A@TQFP64 [DX3011]
PIC24HJ128GP310(ISP) [DX0001]
PIC24HJ128GP310@TQFP100(1) [DX3021]
PIC24HJ128GP310@TQFP100(2) [DX3071]
PIC24HJ128GP310A(ISP) [DX0001]
PIC24HJ128GP310A@TQFP100(1) [DX3021]
PIC24HJ128GP310A@TQFP100(2) [DX3071]
PIC24HJ128GP502 [DX0001]　　PIC24HJ128GP502(ISP) [DX0001]
PIC24HJ128GP502@QFN28 [DX4032]　　PIC24HJ128GP502@SOIC28 [DX1033]
PIC24HJ128GP502@SSOP28 [DX1026]　　PIC24HJ128GP504(ISP) [DX0001]
PIC24HJ128GP504@QFN44 [DX4019]　　PIC24HJ128GP504@TQFP44 [DX3003]
PIC24HJ128GP504@TQFP44(DELTA) [DX3003]
PIC24HJ128GP506(ISP) [DX0001]　　PIC24HJ128GP506@QFN64 [DX4023]
PIC24HJ128GP506@TQFP64 [DX3011]　　PIC24HJ128GP506A(ISP) [DX0001]
PIC24HJ128GP506A@QFN64 [DX4023]　　PIC24HJ128GP506A@TQFP64 [DX3011]
PIC24HJ128GP510(ISP) [DX0001]
PIC24HJ128GP510@TQFP100(1) [DX3021]
PIC24HJ128GP510@TQFP100(2) [DX3071]
PIC24HJ128GP510A(ISP) [DX0001]
PIC24HJ128GP510A@TQFP100(1) [DX3021]
PIC24HJ128GP510A@TQFP100(2) [DX3071]
PIC24HJ12GP201 [DX0001]　　PIC24HJ12GP201(ISP) [DX0001]
PIC24HJ12GP201@SOIC18 [DX1033]
PIC24HJ12GP201@SOIC18(ISP) [DX0001]
PIC24HJ12GP202 [DX0001]　　PIC24HJ12GP202(ISP) [DX0001]
PIC24HJ12GP202@QFN28 [DX4014]
PIC24HJ12GP202@QFN28(ISP) [DX0001]
PIC24HJ12GP202@SOIC28 [DX1033]
PIC24HJ12GP202@SOIC28(ISP) [DX0001]
PIC24HJ12GP202@SSOP28 [DX1026]
PIC24HJ12GP202@SSOP28(ISP) [DX0001]
PIC24HJ16GP304@QFN44 [DX4019]
PIC24HJ16GP304@QFN44(ISP) [DX0001]
PIC24HJ16GP304@TQFP44 [DX3003]
PIC24HJ16GP304@TQFP44(ISP) [DX0001]
PIC24HJ256GP206(ISP) [DX0001]　　PIC24HJ256GP206@QFN64 [DX4023]
PIC24HJ256GP206@TQFP64 [DX3011]　　PIC24HJ256GP206A(ISP) [DX0001]
PIC24HJ256GP206A@QFN64 [DX4023]　　PIC24HJ256GP206A@TQFP64 [DX3011]
PIC24HJ256GP210(ISP) [DX0001]

PIC24HJ256GP210@TQFP100(1) [DX3021]
PIC24HJ256GP210@TQFP100(2) [DX3071]
PIC24HJ256GP210A(ISP) [DX0001]
PIC24HJ256GP210A@TQFP100(1) [DX3021]
PIC24HJ256GP210A@TQFP100(2) [DX3071]
PIC24HJ256GP610(ISP) [DX0001]
PIC24HJ256GP610@TQFP100(1) [DX3021]
PIC24HJ256GP610@TQFP100(2) [DX3071]
PIC24HJ256GP610A(ISP) [DX0001]
PIC24HJ256GP610A@TQFP100(1) [DX3021]
PIC24HJ256GP610A@TQFP100(2) [DX3071]
PIC24HJ32GP202 [DX0001]
PIC24HJ32GP202(ISP) [DX0001]
PIC24HJ32GP202@QFN28 [DX4014]
PIC24HJ32GP202@QFN28(ISP) [DX0001]
PIC24HJ32GP202@SOIC28 [DX1033]
PIC24HJ32GP202@SOIC28(ISP) [DX0001]
PIC24HJ32GP202@SSOP28 [DX1026]
PIC24HJ32GP202@SSOP28(ISP) [DX0001]
PIC24HJ32GP204@QFN44 [DX4019]
PIC24HJ32GP204@QFN44(ISP) [DX0001]
PIC24HJ32GP204@TQFP44 [DX3003]
PIC24HJ32GP204@TQFP44(ISP) [DX0001]
PIC24HJ32GP302 [DX0001]
PIC24HJ32GP302(ISP) [DX0001]
PIC24HJ32GP302@QFN28 [DX4014]
PIC24HJ32GP302@QFN28(ISP) [DX0001]
PIC24HJ32GP302@SOIC28 [DX1033]
PIC24HJ32GP302@SOIC28(ISP) [DX0001]
PIC24HJ32GP302@SSOP28 [DX1026]
PIC24HJ32GP302@SSOP28(ISP) [DX0001]
PIC24HJ32GP304@QFN44 [DX4019]
PIC24HJ32GP304@QFN44(ISP) [DX0001]
PIC24HJ32GP304@TQFP44 [DX3003]
PIC24HJ32GP304@TQFP44(ISP) [DX0001]
PIC24HJ64GP202 [DX0001]
PIC24HJ64GP202(ISP) [DX0001]
PIC24HJ64GP202@QFN28 [DX4014]
PIC24HJ64GP202@QFN28(ISP) [DX0001]
PIC24HJ64GP202@SOIC28 [DX1033]
PIC24HJ64GP202@SOIC28(ISP) [DX0001]
PIC24HJ64GP202@SSOP28 [DX1026]
PIC24HJ64GP202@SSOP28(ISP) [DX0001]
PIC24HJ64GP204@QFN44 [DX4019]
PIC24HJ64GP204@QFN44(ISP) [DX0001]
PIC24HJ64GP204@TQFP44 [DX3003]
PIC24HJ64GP204@TQFP44(ISP) [DX0001]
PIC24HJ64GP206@QFN64 [DX4023]
PIC24HJ64GP206@QFN64(ISP) [DX0001]
PIC24HJ64GP206@TQFP64 [DX3011]
PIC24HJ64GP206@TQFP64(ISP) [DX0001]

PIC24HJ64GP206A@QFN64 [DX4023]
PIC24HJ64GP206A@QFN64(ISP) [DX0001]
PIC24HJ64GP206A@TQFP64 [DX3011]
PIC24HJ64GP206A@TQFP64(ISP) [DX0001]
PIC24HJ64GP210@TQFP100(12)(ISP) [DX0001]
PIC24HJ64GP210@TQFP100(12*12*1) [DX3071]
PIC24HJ64GP210@TQFP100(14)(ISP) [DX0001]
PIC24HJ64GP210@TQFP100(14*14*1) [DX3021]
PIC24HJ64GP210A@TQFP100(12)(ISP) [DX0001]
PIC24HJ64GP210A@TQFP100(12*12*1) [DX3071]
PIC24HJ64GP210A@TQFP100(14)(ISP) [DX0001]
PIC24HJ64GP210A@TQFP100(14*14*1) [DX3021]
PIC24HJ64GP502 [DX0001]　　PIC24HJ64GP502(ISP) [DX0001]
PIC24HJ64GP502@QFN28 [DX4014]
PIC24HJ64GP502@QFN28(ISP) [DX0001]
PIC24HJ64GP502@SOIC28 [DX1033]
PIC24HJ64GP502@SOIC28(ISP) [DX0001]
PIC24HJ64GP502@SSOP28 [DX1026]
PIC24HJ64GP502@SSOP28(ISP) [DX0001]
PIC24HJ64GP504@QFN44 [DX4019]
PIC24HJ64GP504@QFN44(ISP) [DX0001]
PIC24HJ64GP504@TQFP44 [DX3003]
PIC24HJ64GP504@TQFP44(ISP) [DX0001]
PIC24HJ64GP506@QFN64 [DX4023]
PIC24HJ64GP506@QFN64(ISP) [DX0001]
PIC24HJ64GP506@TQFP64 [DX3011]
PIC24HJ64GP506@TQFP64(ISP) [DX0001]
PIC24HJ64GP506A@QFN64 [DX4023]
PIC24HJ64GP506A@QFN64(ISP) [DX0001]
PIC24HJ64GP506A@TQFP64 [DX3011]
PIC24HJ64GP506A@TQFP64(ISP) [DX0001]
PIC24HJ64GP510@TQFP100(12)(ISP) [DX0001]
PIC24HJ64GP510@TQFP100(12*12*1) [DX3071]
PIC24HJ64GP510@TQFP100(14)(ISP) [DX0001]
PIC24HJ64GP510@TQFP100(14*14*1) [DX3021]
PIC24HJ64GP510A@TQFP100(12)(ISP) [DX0001]
PIC24HJ64GP510A@TQFP100(12*12*1) [DX3071]
PIC24HJ64GP510A@TQFP100(14)(ISP) [DX0001]
PIC24HJ64GP510A@TQFP100(14*14*1) [DX3021]
PIC30F1010 [DX0001]　　PIC30F1010@ISP [DX0001]
PIC30F1010@QFN28 [DX4014]　　PIC30F1010@SDIP28 [DX0032]
PIC30F1010@SOIC28 [DX1033]　　PIC30F2010@QFN28 [DX4014]
PIC30F2020 [DX0001]　　PIC30F2020@ISP [DX0001]
PIC30F2020@QFN28 [DX4014]　　PIC30F2020@SDIP28 [DX0032]
PIC30F2020@SOIC28 [DX1033]　　PIC30F2023@ISP [DX0001]
PIC30F2023@QFN44 [DX4014]　　PIC30F2023@TQFP44 [DX3003]
PIC32MX130F064D@TQFP44 [DX3003#2]
PIC32MX320F032H@QFN64 [DX4023#1]

PIC32MX320F032H@TQFP100(12*12*1) [DX3071#1]
PIC32MX320F032H@TQFP100(14*14*1) [DX3021#1]
PIC32MX320F032H@TQFP64 [DX3011#2]
PIC32MX320F064H@QFN64 [DX4023#1]
PIC32MX320F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX320F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX320F064H@TQFP64 [DX3011#2]
PIC32MX320F128H@QFN64 [DX4023#1]
PIC32MX320F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX320F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX320F128H@TQFP64 [DX3011#2]
PIC32MX320F128L@QFN64 [DX4023#1]
PIC32MX320F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX320F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX320F128L@TQFP64 [DX3011#2]
PIC32MX330F064H@QFN64 [DX4023#1]
PIC32MX330F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX330F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX330F064H@TQFP64 [DX3011#2]
PIC32MX330F064L@QFN64 [DX4023#1]
PIC32MX330F064L@TQFP100(12*12*1) [DX3071#1]
PIC32MX330F064L@TQFP100(14*14*1) [DX3021#1]
PIC32MX330F064L@TQFP64 [DX3011#2]
PIC32MX340F128H@QFN64 [DX4023#1]
PIC32MX340F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX340F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX340F128H@TQFP64 [DX3011#2]
PIC32MX340F128L@QFN64 [DX4023#1]
PIC32MX340F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX340F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX340F128L@TQFP64 [DX3011#2]
PIC32MX340F256H@QFN64 [DX4023#1]
PIC32MX340F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX340F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX340F256H@TQFP64 [DX3011#2]
PIC32MX340F512H@QFN64 [DX4023#1]
PIC32MX340F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX340F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX340F512H@TQFP64 [DX3011#2]
PIC32MX350F128H@QFN64 [DX4023#1]
PIC32MX350F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX350F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX350F128H@TQFP64 [DX3011#2]
PIC32MX350F128L@QFN64 [DX4023#1]
PIC32MX350F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX350F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX350F128L@TQFP64 [DX3011#2]
PIC32MX350F256H@QFN64 [DX4023#1]

PIC32MX350F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX350F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX350F256H@TQFP64 [DX3011#2]
PIC32MX350F256L@QFN64 [DX4023#1]
PIC32MX350F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX350F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX350F256L@TQFP64 [DX3011#2]
PIC32MX360F256L@QFN64 [DX4023#1]
PIC32MX360F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX360F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX360F256L@TQFP64 [DX3011#2]
PIC32MX360F512H@QFN64 [DX4023#1]
PIC32MX360F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX360F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX360F512H@TQFP64 [DX3011#2]
PIC32MX360F512L@QFN64 [DX4023#1]
PIC32MX360F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX360F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX360F512L@TQFP64 [DX3011#2]
PIC32MX370F512H@QFN64 [DX4023#1]
PIC32MX370F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX370F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX370F512H@TQFP64 [DX3011#2]
PIC32MX370F512L@QFN64 [DX4023#1]
PIC32MX370F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX370F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX370F512L@TQFP64 [DX3011#2]
PIC32MX430F064H@QFN64 [DX4023#1]
PIC32MX430F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX430F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX430F064H@TQFP64 [DX3011#2]
PIC32MX430F064L@QFN64 [DX4023#1]
PIC32MX430F064L@TQFP100(12*12*1) [DX3071#1]
PIC32MX430F064L@TQFP100(14*14*1) [DX3021#1]
PIC32MX430F064L@TQFP64 [DX3011#2]
PIC32MX440F128H@QFN64 [DX4023#1]
PIC32MX440F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX440F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX440F128H@TQFP64 [DX3011#2]
PIC32MX440F128L@QFN64 [DX4023#1]
PIC32MX440F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX440F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX440F128L@TQFP64 [DX3011#2]
PIC32MX440F256H@QFN64 [DX4023#1]
PIC32MX440F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX440F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX440F256H@TQFP64 [DX3011#2]
PIC32MX440F512H@QFN64 [DX4023#1]

PIC32MX440F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX440F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX440F512H@TQFP64 [DX3011#2]
PIC32MX450F128H@QFN64 [DX4023#1]
PIC32MX450F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX450F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX450F128H@TQFP64 [DX3011#2]
PIC32MX450F128L@QFN64 [DX4023#1]
PIC32MX450F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX450F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX450F128L@TQFP64 [DX3011#2]
PIC32MX450F256H@QFN64 [DX4023#1]
PIC32MX450F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX450F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX450F256H@TQFP64 [DX3011#2]
PIC32MX450F256L@QFN64 [DX4023#1]
PIC32MX450F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX450F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX450F256L@TQFP64 [DX3011#2]
PIC32MX460F256L@QFN64 [DX4023#1]
PIC32MX460F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX460F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX460F256L@TQFP64 [DX3011#2]
PIC32MX460F512L@QFN64 [DX4023#1]
PIC32MX460F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX460F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX460F512L@TQFP64 [DX3011#2]
PIC32MX470F512H@QFN64 [DX4023#1]
PIC32MX470F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX470F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX470F512H@TQFP64 [DX3011#2]
PIC32MX470F512L@QFN64 [DX4023#1]
PIC32MX470F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX470F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX470F512L@TQFP64 [DX3011#2]
PIC32MX534F064H@QFN64 [DX4023#1]
PIC32MX534F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX534F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX534F064H@TQFP64 [DX3011#2]
PIC32MX534F064L@QFN64 [DX4023#1]
PIC32MX534F064L@TQFP100(12*12*1) [DX3071#1]
PIC32MX534F064L@TQFP100(14*14*1) [DX3021#1]
PIC32MX534F064L@TQFP64 [DX3011#2]
PIC32MX564F064H@QFN64 [DX4023#1]
PIC32MX564F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX564F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX564F064H@TQFP64 [DX3011#2]
PIC32MX564F064L@QFN64 [DX4023#1]

PIC32MX564F064L@TQFP100(12*12*1) [DX3071#1]
PIC32MX564F064L@TQFP100(14*14*1) [DX3021#1]
PIC32MX564F064L@TQFP64 [DX3011#2]
PIC32MX564F128H@QFN64 [DX4023#1]
PIC32MX564F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX564F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX564F128H@TQFP64 [DX3011#2]
PIC32MX564F128L@QFN64 [DX4023#1]
PIC32MX564F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX564F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX564F128L@TQFP64 [DX3011#2]
PIC32MX575F256H@QFN64 [DX4023#1]
PIC32MX575F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX575F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX575F256H@TQFP64 [DX3011#2]
PIC32MX575F256L@QFN64 [DX4023#1]
PIC32MX575F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX575F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX575F256L@TQFP64 [DX3011#2]
PIC32MX575F512H@QFN64 [DX4023#1]
PIC32MX575F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX575F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX575F512H@TQFP64 [DX3011#2]
PIC32MX575F512L@QFN64 [DX4023#1]
PIC32MX575F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX575F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX575F512L@TQFP64 [DX3011#2]
PIC32MX664F064H@QFN64 [DX4023#1]
PIC32MX664F064H@TQFP100(12*12*1) [DX3071#1]
PIC32MX664F064H@TQFP100(14*14*1) [DX3021#1]
PIC32MX664F064H@TQFP64 [DX3011#2]
PIC32MX664F064L@QFN64 [DX4023#1]
PIC32MX664F064L@TQFP100(12*12*1) [DX3071#1]
PIC32MX664F064L@TQFP100(14*14*1) [DX3021#1]
PIC32MX664F064L@TQFP64 [DX3011#2]
PIC32MX664F128H@QFN64 [DX4023#1]
PIC32MX664F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX664F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX664F128H@TQFP64 [DX3011#2]
PIC32MX664F128L@QFN64 [DX4023#1]
PIC32MX664F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX664F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX664F128L@TQFP64 [DX3011#2]
PIC32MX675F256H@QFN64 [DX4023#1]
PIC32MX675F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX675F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX675F256H@TQFP64 [DX3011#2]
PIC32MX675F256L@QFN64 [DX4023#1]

PIC32MX675F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX675F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX675F256L@TQFP64 [DX3011#2]
PIC32MX675F512H@QFN64 [DX4023#1]
PIC32MX675F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX675F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX675F512H@TQFP64 [DX3011#2]
PIC32MX675F512L@QFN64 [DX4023#1]
PIC32MX675F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX675F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX675F512L@TQFP64 [DX3011#2]
PIC32MX695F512H@QFN64 [DX4023#1]
PIC32MX695F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX695F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX695F512H@TQFP64 [DX3011#2]
PIC32MX695F512L@QFN64 [DX4023#1]
PIC32MX695F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX695F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX695F512L@TQFP64 [DX3011#2]
PIC32MX764F128H@QFN64 [DX4023#1]
PIC32MX764F128H@TQFP100(12*12*1) [DX3071#1]
PIC32MX764F128H@TQFP100(14*14*1) [DX3021#1]
PIC32MX764F128H@TQFP64 [DX3011#2]
PIC32MX764F128L@QFN64 [DX4023#1]
PIC32MX764F128L@TQFP100(12*12*1) [DX3071#1]
PIC32MX764F128L@TQFP100(14*14*1) [DX3021#1]
PIC32MX764F128L@TQFP64 [DX3011#2]
PIC32MX775F256H@QFN64 [DX4023#1]
PIC32MX775F256H@TQFP100(12*12*1) [DX3071#1]
PIC32MX775F256H@TQFP100(14*14*1) [DX3021#1]
PIC32MX775F256H@TQFP64 [DX3011#2]
PIC32MX775F256L@QFN64 [DX4023#1]
PIC32MX775F256L@TQFP100(12*12*1) [DX3071#1]
PIC32MX775F256L@TQFP100(14*14*1) [DX3021#1]
PIC32MX775F256L@TQFP64 [DX3011#2]
PIC32MX775F512H@QFN64 [DX4023#1]
PIC32MX775F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX775F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX775F512H@TQFP64 [DX3011#2]
PIC32MX775F512L@QFN64 [DX4023#1]
PIC32MX775F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX775F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX775F512L@TQFP64 [DX3011#2]
PIC32MX795F512H@QFN64 [DX4023#1]
PIC32MX795F512H@TQFP100(12*12*1) [DX3071#1]
PIC32MX795F512H@TQFP100(14*14*1) [DX3021#1]
PIC32MX795F512H@TQFP64 [DX3011#2]
PIC32MX795F512L@QFN64 [DX4023#1]

PIC32MX795F512L@TQFP100(12*12*1) [DX3071#1]
PIC32MX795F512L@TQFP100(14*14*1) [DX3021#1]
PIC32MX795F512L@TQFP64 [DX3011#2]
PIC32MZ1024ECG@TQFP144 [DX3035#1]
PIC32MZ1024ECH@TQFP144 [DX3035#1]
PIC32MZ1024ECM@TQFP144 [DX3035#1]
PIC32MZ1024EFG@TQFP144 [DX3035#1]
PS200 [DX0001]
PS200(ISP) [DX0001]
PS200@SOIC20 [DX1033]
PS200@SOIC20(ISP) [DX0001]
PS200@SSOP20 [DX1026]
PS200@SSOP20(ISP) [DX0001]
rfPIC12C509AF@SSOP20 [DX1026]
rfPIC12C509AF@SSOP20(ISP) [DX0001]
rfPIC12C509AG@SOIC18 [DX1033]
rfPIC12C509AG@SOIC18(ISP) [DX0001]
rfPIC12LC509AF@SSOP20 [DX1026]
rfPIC12LC509AF@SSOP20(ISP) [DX0001]
rfPIC12LC509AG@SOIC18 [DX1033]
rfPIC12LC509AG@SOIC18(ISP) [DX0001]

MICROCHIP(SST)

E(E)PROM/FRAM/NVRAM

SST25LF010@SOIC8(4.0) [DX1045-1]
SST25LF010@SOIC8(5.4) [DX1044-1]
SST25LF010@WSON8 [DX4005-1]
SST25LF010A@SOIC8(4.0) [DX1045-1]
SST25LF010A@SOIC8(5.4) [DX1044-1]
SST25LF010A@WSON8 [DX4005-1]
SST25LF016A@SOIC8(4.0) [DX1045#1]
SST25LF016A@SOIC8(5.4) [DX1044#1]
SST25LF016A@WSON8 [DX4005#1]
SST25LF016B@SOIC8(4.0) [DX1045#1]
SST25LF016B@SOIC8(5.4) [DX1044#1]
SST25LF016B@WSON8 [DX4005#1]
SST25LF020@SOIC8(4.0) [DX1045-1]
SST25LF020@SOIC8(5.4) [DX1044-1]
SST25LF020@WSON8 [DX4005-1]
SST25LF020A@SOIC8(4.0) [DX1045-1]
SST25LF020A@SOIC8(5.4) [DX1044-1]
SST25LF020A@WSON8 [DX4005-1]
SST25LF040@SOIC8(4.0) [DX1045-1]
SST25LF040@SOIC8(5.4) [DX1044-1]
SST25LF040@WSON8 [DX4005-1]
SST25LF040A@SOIC8(4.0) [DX1045-1]
SST25LF040A@SOIC8(5.4) [DX1044-1]
SST25LF040A@WSON8 [DX4005-1]
SST25LF080@SOIC8(4.0) [DX1045-1]
SST25LF080@SOIC8(5.4) [DX1044-1]
SST25LF080@WSON8 [DX4005-1]
SST25LF080A@SOIC8(4.0) [DX1045-1]
SST25LF080A@SOIC8(5.4) [DX1044-1]
SST25LF080A@WSON8 [DX4005-1]
SST25VF010@SOIC8(4.0) [DX1045-1]
SST25VF010@SOIC8(5.4) [DX1044-1]
SST25VF010@WSON8 [DX4005-1]

SST25VF010A@SOIC8(4.0) [DX1045-1]
SST25VF010A@SOIC8(5.4) [DX1044-1]
SST25VF010A@WSON8 [DX4005-1]
SST25VF016B@SOIC8(4.0) [DX1045#1]
SST25VF016B@SOIC8(5.4) [DX1044#1]
SST25VF016B@WSON8 [DX4005#1]
SST25VF020@SOIC8(4.0) [DX1045-1]
SST25VF020@SOIC8(5.4) [DX1044-1]
SST25VF020@WSON8 [DX4005-1]
SST25VF020B@SOIC8(4.0) [DX1045#1]
SST25VF020B@SOIC8(5.4) [DX1044#1]
SST25VF020B@WSON8 [DX4005#1]
SST25VF032B@SOIC16 [DX1033#1]
SST25VF032B@SOIC8(4.0) [DX1045#1]
SST25VF032B@SOIC8(5.4) [DX1044#1]
SST25VF032B@WSON8 [DX4005#1]
SST25VF040@SOIC8(4.0) [DX1045-1]
SST25VF040@SOIC8(5.4) [DX1044-1]
SST25VF040@WSON8 [DX4005-1]
SST25VF040B@SOIC8(4.0) [DX1045#1]
SST25VF040B@SOIC8(5.4) [DX1044#1]
SST25VF040B@WSON8 [DX4005#1]
SST25VF064C@SOIC16 [DX1033#1]
SST25VF064C@SOIC8 [DX1044#1]
SST25VF064C@WSON8 [DX4006#1]
SST25VF080@SOIC8(4.0) [DX1045-1]
SST25VF080@SOIC8(5.4) [DX1044-1]
SST25VF080@WSON8 [DX4005-1]
SST25VF080B@SOIC8(4.0) [DX1045#1]
SST25VF080B@SOIC8(5.4) [DX1044#1]
SST25VF080B@WSON8 [DX4005#1]
SST25VF512@SOIC8(4.0) [DX1045-1]
SST25VF512@SOIC8(5.4) [DX1044-1]
SST25VF512@WSON8 [DX4005-1]
SST25VF512A@SOIC8(4.0) [DX1045-1]
SST25VF512A@SOIC8(5.4) [DX1044-1]
SST25VF512A@WSON8 [DX4005-1]
SST25WF010@SOIC8(4.0) [DX1045-1]
SST25WF010@SOIC8(5.4) [DX1044-1]
SST25WF010@WSON8 [DX4005-1]
SST25WF020@SOIC8(4.0) [DX1045-1]
SST25WF020@SOIC8(5.4) [DX1044-1]
SST25WF020@WSON8 [DX4005-1]
SST25WF020A@SOIC8(4.0) [DX1045#1]
SST25WF020A@SOIC8(5.4) [DX1044#1]
SST25WF020A@WSON8 [DX4005#1]
SST25WF040@SOIC8(4.0) [DX1045-1]
SST25WF040@SOIC8(5.4) [DX1044-1]
SST25WF040@WSON8 [DX4005-1]
SST25WF080@SOIC8(4.0) [DX1045-1]
SST25WF080@SOIC8(5.4) [DX1044-1]
SST25WF080@WSON8 [DX4005-1]
SST25WF080B@SOIC8(4.0) [DX1045-1]
SST25WF080B@SOIC8(5.4) [DX1044-1]
SST25WF080B@WSON8 [DX4005-1]
SST25WF512@SOIC8(4.0) [DX1045-1]
SST25WF512@SOIC8(5.4) [DX1044-1]
SST25WF512@WSON8 [DX4005-1]
SST26VF064B@SOIC16 [DX1033#1]
SST26VF064B@SOIC8 [DX1044#1]
SST26VF064B@TFBGA24 [DX5146]
SST26VF064B@WDFN8 [DX4006#1]
SST26VF064BA@SOIC16 [DX1033#1]
SST26VF064BA@SOIC8 [DX1044#1]
SST26VF064BA@TFBGA24 [DX5146]
SST26VF064BA@WDFN8 [DX4006#1]

MICRON

E(E)PROM/FRAM/NVRAM

DT28F640J3@SSOP56 [DX0051]
M25P05-A@TSSOP8 [DX1059#3]
M25P05-A@VFQFPN8 [DX4005#1]
M25P10-A@UFDFPN8 [DX4002#1]
M25P16 [DX0001]
M25P16@SO8N [DX1045#1]
M25P16MC@UFDFPN8 [DX4081]
M25P16MP@VFDFPN8 [DX4005#1]
M25P20@SO8 [DX1045#1]
M25P32@SO16 [DX1072#1]
M25P32@VFDFPN8 [DX4006#1]
M25P40@DFN8 [DX4005#1]
M25P40@SO8W [DX1044#1]
M25P40MB@UFDFPN8 [DX4002#1]
M25P64@SO16 [DX1072#1]
M25P80 [DX0001]
M25P80@SO8W [DX1044#1]
M25P80@VFDFPN8 [DX4005#1]
M25PE10@VFQFPN8 [DX4005#1]
M25PE16@VFQFPN8 [DX4005#1]
M25PE20@VFQFPN8 [DX4005#1]
M25PE40@SO8W [DX1044#1]
M25PE80@QFN8L [DX4005#1]
M25PE80@SO8W [DX1044#1]
M29W512GH@TSOP56 [DX1055]
M45PE10@VFQPN8 [DX4005#1]
M45PE16@VFQFPN8 [DX4005#1]
M45PE20@VFQFPN8 [DX4005#1]
M45PE40@SO8W [DX1044#1]
M45PE80@QFN8L [DX4005#1]
M45PE80@SO8W [DX1044#1]
MT25QL01GBBA8E12 [DX5157]
MT25QL128ABA1E14 [DX5157]
MT25QL128ABA1ESF [DX1072#1]
MT25QL128ABA1EW9 [DX4006#1]
MT25QL512ABA1E12 [DX5157]
MT25QL512ABA8E12 [DX5157]
MT25QU01GBBA8E12 [DX5157]
MT25QU128ABA1ESE [DX5157]
MT25QU512ABA1E12 [DX5157]
MT25QU512ABA8E12 [DX5157]
MT25QU512ABB8ESF [DX1033#1]
MT28EW01GABA1HJS0@TSOP56 [DX1055]
MT28EW01GABA1HJS1@TSOP56 [DX1055]
MT28EW01GABA1HPC0@FBGA64 [DX5074]
MT28EW01GABA1HPC1@FBGA64 [DX5074]
M25P05-A@SO8 [DX1045#1]
M25P05-A@UFDFPN8 [DX4002#1]
M25P10-A@SO8 [DX1045#1]
M25P10-A@VFQFPN8 [DX4005#1]
M25P16@SO16 [DX1072#1]
M25P16@SO8W [DX1044#1]
M25P16ME@VFDFPN8 [DX4006#1]
M25P20@QFN8L [DX4005#1]
M25P20@VFQFPN8 [DX4005#1]
M25P32@SO8W [DX1044#1]
M25P32@VFQFPN8 [DX4005#1]
M25P40@SO8N [DX1045#1]
M25P40@VFDFPN8 [DX4005#1]
M25P40MC@UFDFPN8 [DX4076]
M25P64@VDFPN8 [DX4006#1]
M25P80@SO8N [DX1045#1]
M25P80@UFDFPN8 [DX4076]
M25PE10@SO8N [DX1045#1]
M25PE16@SO8W [DX1044#1]
M25PE20@SO8N [DX1045#1]
M25PE40@SO8N [DX1045#1]
M25PE40@VFQFPN8 [DX4005#1]
M25PE80@SO8N [DX1045#1]
M25PE80@VFQFPN8 [DX4005#1]
M45PE10@SO8N [DX1045#1]
M45PE16@SO8W [DX1044#1]
M45PE20@SO8 [DX1045#1]
M45PE40@SO8N [DX1045#1]
M45PE40@VFQFPN8 [DX4005#1]
M45PE80@SO8N [DX1045#1]
M45PE80@VFQFPN8 [DX4005#1]
MT25QL128ABA1E12 [DX5157]
MT25QL128ABA1ESE [DX5157]
MT25QL128ABA1EW7 [DX4005#1]
MT25QL256ABA8E12 [DX5157]
MT25QL512ABA1ESF [DX1033#1]
MT25QL512ABA8ESF [DX1033#1]
MT25QU128ABA1E12 [DX5157]
MT25QU128ABA1ESF [DX1072#1]
MT25QU512ABA1ESF [DX1033#1]
MT25QU512ABA8ESF [DX1033#1]

MT28EW01GABA1LJS0@TSOP56 [DX1055]
MT28EW01GABA1LJS1@TSOP56 [DX1055]
MT28EW01GABA1LPC0@FBGA64 [DX5074]
MT28EW01GABA1LPC1@FBGA64 [DX5074]
MT28EW128ABA1HJS@TSOP56 [DX1055]　　MT28EW128ABA1HPC@FBGA64 [DX5074]
MT28EW128ABA1LJS@TSOP56 [DX1055]　　MT28EW128ABA1LPC@FBGA64 [DX5074]
MT28EW256ABA1HJS@TSOP56 [DX1055]　　MT28EW256ABA1HPC@FBGA64 [DX5074]
MT28EW256ABA1HPN@FBGA56 [DX5045]　　MT28EW256ABA1LJS@TSOP56 [DX1055]
MT28EW256ABA1LPC@FBGA64 [DX5074]　　MT28EW256ABA1LPN@FBGA56 [DX5045]
MT28EW512ABA1HJS@TSOP56 [DX1055]　　MT28EW512ABA1HPC@FBGA64 [DX5074]
MT28EW512ABA1HPN@FBGA56 [DX5045]　　MT28EW512ABA1LJS@TSOP56 [DX1055]
MT28EW512ABA1LPC@FBGA64 [DX5074]　　MT28EW512ABA1LPN@FBGA56 [DX5045]
MT28F002B1VG-B@TSOP40 [DX1006]　　MT28F002B1VG-T@TSOP40 [DX1006]
MT28F002B3VG-B@TSOP40 [DX1006]　　MT28F002B3VG-T@TSOP40 [DX1006]
MT28F002B5VG-B@TSOP40 [DX1006]　　MT28F002B5VG-T@TSOP40 [DX1006]
MT28F002C1VG-T@TSOP40 [DX1006]　　MT28F002C5VG-T@TSOP40 [DX1006]
MT28F002VG-B@TSOP40 [DX1006]　　MT28F002VG-T@TSOP40 [DX1006]
MT28F004B1VG-B@TSOP40 [DX1006]　　MT28F004B1VG-T@TSOP40 [DX1006]
MT28F004B3VG-B@TSOP40 [DX1006]　　MT28F004B3VG-T@TSOP40 [DX1006]
MT28F004B5VG-B@TSOP40 [DX1006]　　MT28F004B5VG-T@TSOP40 [DX1006]
MT28F004VG-B@TSOP40 [DX1006]　　MT28F004VG-T@TSOP40 [DX1006]
MT28F008B1VG-B@TSOP40 [DX1006]　　MT28F008B1VG-T@TSOP40 [DX1006]
MT28F008B3VG-B@TSOP40 [DX1006]　　MT28F008B3VG-T@TSOP40 [DX1006]
MT28F008B5VG-B@TSOP40 [DX1006]　　MT28F008B5VG-T@TSOP40 [DX1006]
MT28F016S3VG@TSOP40 [DX1006]　　MT28F016S5VG@TSOP40 [DX1006]
MT28F128J3A(FW203)(I.)@FBGA64 [DX5004]
MT28F128J3A(FW501)(I.)@FBGA64 [DX5004]
MT28F128J3A(FW502)(M.)@FBGA64 [DX5004]
MT28F128J3A(FW503)(M.)@FBGA64 [DX5004]
MT28F128J3A(INTEL)@TSOP56 [DX1011]
MT28F128J3A(MICRON)@TSOP56 [DX1011]
MT28F200B1SGB@PSOP44 [DX1014]　　MT28F200B1SGT@PSOP44 [DX1014]
MT28F200B1WGB@TSOP48 [DX1004]　　MT28F200B1WGT@TSOP48 [DX1004]
MT28F200B3SGB@PSOP44 [DX1014]　　MT28F200B3SGT@PSOP44 [DX1014]
MT28F200B3WGB@TSOP48 [DX1004]　　MT28F200B3WGT@TSOP48 [DX1004]
MT28F200B5SGB@PSOP44 [DX1014]　　MT28F200B5SGT@PSOP44 [DX1014]
MT28F200B5WGB@TSOP48 [DX1004]　　MT28F200B5WGT@TSOP48 [DX1004]
MT28F320J3A(FW201)(I.)@FBGA64 [DX5004]
MT28F320J3A(FW204)(M.)@FBGA64 [DX5004]
MT28F320J3A(FW207)(I.)@FBGA64 [DX5004]
MT28F320J3A(FW208)(M.)@FBGA64 [DX5004]
MT28F320J3A(INTEL)@TSOP56 [DX1011]
MT28F320J3A(MICRON)@TSOP56 [DX1011]
MT28F322D18FH(BET)(FW536)@FBGA58 [DX5014]
MT28F322D18FH(BET)(FW538)@FBGA58 [DX5014]
MT28F322D18FH(BET)(FW542)@FBGA58 [DX5014]
MT28F322D18FH(BET)(FW556)@FBGA58 [DX5014]
MT28F322D18FH(BET)(FW559)@FBGA58 [DX5014]

MT28F322D18FH(TET)(FW535)@FBGA58 [DX5014]
MT28F322D18FH(TET)(FW537)@FBGA58 [DX5014]
MT28F322D18FH(TET)(FW543)@FBGA58 [DX5014]
MT28F322D18FH(TET)(FW557)@FBGA58 [DX5014]
MT28F322D18FH(TET)(FW558)@FBGA58 [DX5014]
MT28F322D20FH(BET)(FW547)@FBGA58 [DX5014]
MT28F322D20FH(BET)(FW549)@FBGA58 [DX5014]
MT28F322D20FH(BET)(FW550)@FBGA58 [DX5014]
MT28F322D20FH(BET)(FW552)@FBGA58 [DX5014]
MT28F322D20FH(TET)(FW546)@FBGA58 [DX5014]
MT28F322D20FH(TET)(FW548)@FBGA58 [DX5014]
MT28F322D20FH(TET)(FW551)@FBGA58 [DX5014]
MT28F322D20FH(TET)(FW553)@FBGA58 [DX5014]
MT28F400B1SGB@PSOP44 [DX1014]　　MT28F400B1SGT@PSOP44 [DX1014]
MT28F400B1WGB@TSOP48 [DX1004]　　MT28F400B1WGT@TSOP48 [DX1004]
MT28F400B3SGB@PSOP44 [DX1014]　　MT28F400B3SGT@PSOP44 [DX1014]
MT28F400B3WGB@TSOP48 [DX1004]　　MT28F400B3WGT@TSOP48 [DX1004]
MT28F400B5SGB@PSOP44 [DX1014]　　MT28F400B5SGT@PSOP44 [DX1014]
MT28F400B5WGB@TSOP48 [DX1004]　　MT28F400B5WGT@TSOP48 [DX1004]
MT28F640J3A(FW202)(I.)@FBGA64 [DX5004]
MT28F640J3A(FW205)(M.)@FBGA64 [DX5004]
MT28F640J3A(FW206)(I.)@FBGA64 [DX5004]
MT28F640J3A(FW209)(M.)@FBGA64 [DX5004]
MT28F640J3A(FW505)(I.)@FBGA64 [DX5004]
MT28F640J3A(FW506)(M.)@FBGA64 [DX5004]
MT28F640J3A(INTEL)@TSOP56 [DX1011]
MT28F640J3A(MICRON)@TSOP56 [DX1011]
MT28F800B1SGB@PSOP44 [DX1014]　　MT28F800B1SGT@PSOP44 [DX1014]
MT28F800B1WGB@TSOP48 [DX1004]　　MT28F800B1WGT@TSOP48 [DX1004]
MT28F800B3SGB@PSOP44 [DX1014]　　MT28F800B3SGT@PSOP44 [DX1014]
MT28F800B3WGB@TSOP48 [DX1004]　　MT28F800B3WGT@TSOP48 [DX1004]
MT28F800B5SGB@PSOP44 [DX1014]　　MT28F800B5SGT@PSOP44 [DX1014]
MT28F800B5WGB@TSOP48 [DX1004]　　MT28F800B5WGT@TSOP48 [DX1004]
MT28GU01GAAA1EGC@FBGA64 [DX5019]　　MT28GU256AAA1EGC@FBGA64 [DX5019]
MT28GU512AAA1EGC@FBGA64 [DX5019]
MT29C1G12MAACAFAKD@FBGA107 [DX5011-1]
MT29C1G12MAACYAMD@FBGA130 [DX5140-1]
MT29C1G12MAACYAMD@FBGA130(ECC) [DX5140]
MT29C1G12MAADVAKC@FBGA107 [DX5028]
MT29C1G12MAADVAMD@FBGA130 [DX5140-1]
MT29C1G12MAADYAMD@FBGA130 [DX5140]
MT29C1G12MAAIVAMD@FBGA130 [DX5140]
MT29C1G12MAAJVAMD@FBGA130 [DX5140-1]
MT29C1G12MACNAJC@FBGA107 [DX5028]
MT29C1G12MACPAJC@FBGA107 [DX5028]
MT29C1G12MADNAJC@FBGA107 [DX5028]
MT29C1G12MAURAJA@FBGA137 [DX5011-1]
MT29C1G12MAUTAJA@FBGA137 [DX5011]

MT29C1G12MAVNAJC@FBGA107 [DX5028]
MT29C1G12MAVRAJA@FBGA137 [DX5011]
MT29C1G24MADLAJA@FBGA137 [DX5011]
MT29C1G56MAADAAAKC@FBGA107 [DX5028]
MT29C1G56MAADAAAMD@FBGA130 [DX5140-1]
MT29C1G56MACEAJC@FBGA107 [DX5028]
MT29C1G56MACFAJC@FBGA107 [DX5028]
MT29C1G56MADEAJC@FBGA107 [DX5028]
MT29C1G56MAUAAAJC@FBGA107 [DX5028]
MT29C1G56MAUAAAMD@FBGA130 [DX5140]
MT29C1G56MAUAVAKD@FBGA137 [DX5011]
MT29C1G56MAUZAJC@FBGA107 [DX5028]
MT29C1G56MAVAAA@FBGA107 [DX5028]
MT29C1G56MAVAAAJC@FBGA107 [DX5028-1]
MT29C2G24MAAAAHAMD@FBGA130 [DX5140]
MT29C2G24MAAAAKA@FBGA130 [DX5140]
MT29C2G24MAABAHAKC@FBGA107 [DX5028]
MT29C2G24MAABAHAMD@FBGA130 [DX5140-1]
MT29C2G24MAABAKAKD@FBGA137 [DX5011-1]
MT29C2G24MAKJAJC@FBGA107 [DX5028]
MT29C2G24MAKLAJA@FBGA137 [DX5011]
MT29C2G48MAJLCJA@FBGA137 [DX5011]
MT29C2G48MAKJCJC@FBGA107 [DX5028]
MT29C2G48MAKLCJA@FBGA137 [DX5011]
MT29C4G48MAAHBAAKS@FBGA137 [DX5011-1]
MT29C4G48MAPLCJA@FBGA137 [DX5011]
MT29C4G48MAZAPAKD@FBGA137 [DX5011]
MT29C4G48MAZBAAK@BGA168 [DX5205]
MT29C4G48MAZBAAKS@FBGA137 [DX5011-1]
MT29C4G96MAZAPCJA@FBGA137 [DX5011]
MT29C4G96MAZAPCMJ@FBGA240 [DX5185]
MT29C4G96MAZBACJ@BGA168 [DX5205]
MT29C4G96MAZBACKD@FBGA137 [DX5011-1]
MT29C8G72MAPATFJ@FBGA137 [DX5011-1]
MT29C8G96MAYAPDJA@FBGA137 [DX5011-1]
MT29C8G96MAZAPDJA@FBGA137 [DX5011-1]
MT29C8G96MAZBADKD@FBGA137 [DX5011-1]
MT29F128G08AJAAAWP@TSOP48 [DX1004-3]
MT29F16G08ABABA@TSOP48 [DX1004-1]
MT29F16G08CBABA@TSOP48 [DX1004-1]
MT29F16G08CBACA@TSOP48 [DX1004-3]
MT29F16G08FAAWC@TSOP48 [DX1004]
MT29F1G08AACWP@TSOP48 [DX1004]
MT29F1G08ABADA@TSOP48 [DX1004-3]
MT29F1G08ABADAH4@FBGA63 [DX5046-1]
MT29F1G08ABAEA@TSOP48 [DX1004-3]
MT29F1G08ABAEAH4@FBGA63 [DX5046-1]
MT29F1G08ABAWP@TSOP48 [DX1004]
MT29F1G08ABBDAH4@FBGA63 [DX5046-1]

MT29F1G08ABBEAH4@FBGA63 [DX5046-1]
MT29F1G08ABBHC@FBGA63 [DX5028]
MT29F1G08ABCH4@FBGA63 [DX5046]
MT29F1G08ABCHC@FBGA63 [DX5028]
MT29F1G16ABAWP@TSOP48 [DX1004]
MT29F1G16ABBDAH4@FBGA63 [DX5046-1]
MT29F1G16ABBHC@FBGA63 [DX5028]
MT29F1G16ABCH4@FBGA63 [DX5046]
MT29F1G16ABCHC@FBGA63 [DX5028]
MT29F2G08AAAWG@TSOP48 [DX1004]
MT29F2G08AACWP@TSOP48 [DX1004-1]
MT29F2G08AADWP@TSOP48 [DX1004-1]
MT29F2G08ABAEA@TSOP48 [DX1004-3]
MT29F2G08ABAEAH4@FBGA63 [DX5046]
MT29F2G08ABBEAH4@FBGA63 [DX5046]
MT29F2G08ABBEAHC@FBGA63 [DX5028]
MT29F2G08ABDHC@FBGA63 [DX5028]
MT29F2G08ABDWP@TSOP48 [DX1004-1]
MT29F2G16AABWP@TSOP48 [DX1004]
MT29F2G16AADWP@TSOP48 [DX1004]
MT29F2G16ABAEAWP@TSOP48 [DX1004-1]
MT29F2G16ABBEAH4@FBGA63 [DX5046-1]
MT29F2G16ABBEAHC@FBGA63 [DX5028]
MT29F2G16ABDHC@FBGA63 [DX5028]
MT29F32G08ABAAAWP@TSOP48 [DX1004-3]
MT29F32G08AFACAWP(2G)@TSOP48 [DX1004-3]
MT29F32G08CBACAWP(full)@TSOP48 [DX1004-3]
MT29F32G08CBACAWP@TSOP48 [DX1004-3]
MT29F32G08CBADAWP@TSOP48 [DX1004-3]
MT29F4G08AAAWP@TSOP48 [DX1004]
MT29F4G08AACWC@TSOP48 [DX1004-1]
MT29F4G08AACWP@TSOP48 [DX1004-1]
MT29F4G08ABADAH4@FBGA63 [DX5046]
MT29F4G08ABADAWP@TSOP48 [DX1004-1]
MT29F4G08ABAEAH4@BGA63 [DX5046]
MT29F4G08ABAEAWP@TSOP48 [DX1004-3]
MT29F4G08ABBDAH4@FBGA63 [DX5046]
MT29F4G08ABBDAHC@FBGA63 [DX5028]
MT29F4G08ABBEAH4@BGA63 [DX5046]
MT29F4G08ABCHC@FBGA63 [DX5028]
MT29F4G08ABCWC@TSOP48 [DX1004-1]
MT29F4G08BABWP@TSOP48 [DX1004]
MT29F4G16ABADAWP@TSOP48 [DX1004-1]
MT29F4G16ABBDAH4@FBGA63 [DX5046]
MT29F4G16ABBDAHC@FBGA63 [DX5028]
MT29F4G16ABCHC@FBGA63 [DX5028]
MT29F64G08AFAAAWP@TSOP48 [DX1004-3]
MT29F64G08AJABAWP@TSOP48 [DX1004-3]
MT29F64G08CBAAAWP@TSOP48 [DX1004-1]
MT29F64G08CBACAWP@TSOP48 [DX1004-3]
MT29F64G08CBADAWP@TSOP48 [DX1004-3]
MT29F64G08CFABAWP(1G)@TSOP48 [DX1004-3]
MT29F8G08AAAWP@TSOP48 [DX1004-1]
MT29F8G08ABABAWP@TSOP48 [DX1004-3]
MT29F8G08ABACAH4@FBGA63 [DX5046-1]
MT29F8G08ABACAWP@TSOP48 [DX1004-3]
MT29F8G08ADADAH4@FBGA63 [DX5046]
MT29F8G08ADBDAH4@FBGA63 [DX5046]
MT29F8G08MADWC@TSOP48 [DX1004-1]
MT29F8G16ADADAH4@FBGA63 [DX5046]
MT29F8G16ADBDAH4@FBGA63 [DX5046]
MT38L5041A20319Z@FBGA64 [DX5066]
MTFC16GKQDI(16G)@FBGA169 [DX5113]
MTFC16GKQDI(20M)@FBGA169 [DX5113]
MTFC16GKQDI@FBGA169 [DX5113]
MTFC1GDKDM@FBGA153 [DX5104]
MTFC2GGQDI(20M)@FBGA169 [DX5113]
MTFC2GGQDI(2G)@FBGA169 [DX5113]
MTFC2GGQDI@FBGA169 [DX5113]
MTFC2GGQDM(20M)@FBGA153 [DX5104]

MTFC2GGQDM(2G)@FBGA153 [DX5104]
MTFC2GGQDM@FBGA153 [DX5104]
MTFC2GMTEA@FBGA153 [DX5104]
MTFC32GKQDN(20M)@FBGA169 [DX5170]
MTFC32GKQDN(32G)@FBGA169 [DX5170]
MTFC32GKQDN@FBGA169 [DX5170]
MTFC4GACAANA(256MB)@BGA100 [DX5104]
MTFC4GDKDI@FBGA153 [DX5113]
MTFC4GGQDI(20M)@FBGA169 [DX5113]
MTFC4GGQDI(4G)@FBGA169 [DX5113]
MTFC4GGQDI@FBGA169 [DX5113]
MTFC4GGQDM(20M)@FBGA153 [DX5104]
MTFC4GGQDM(4G)@FBGA153 [DX5104]
MTFC4GGQDM@FBGA153 [DX5104]
MTFC4GLTEA@FBGA153 [DX5104]
MTFC4GLVEA@FBGA153 [DX5104]
MTFC8GKQDI(20M)@FBGA169 [DX5113]
MTFC8GKQDI(8G)@FBGA169 [DX5113]
MTFC8GKQDI@FBGA169 [DX5113]
MTFC8GLVEA@BGA153 [DX5104]
N25Q008A@DFN8 [DX4081]
N25Q008A@SOP8 [DX1045#1]
N25Q008A@UFDFPN8 [DX4005#1]
N25Q008A@XFCSP8 [DX5221]
N25Q00AA13G1240F [DX5157]
N25Q00AA13G1240X [DX5157]
N25Q00AA13GSF40F [DX1033#1]
N25Q00AA13GSF40G [DX1033#1]
N25Q016A11E5140F [DX5221]
N25Q016A11ESC40F [DX1044#1]
N25Q016A11ESC40G [DX1045#1]
N25Q032A11EF640E [DX4005#1]
N25Q032A11EF640F [DX4005#1]
N25Q032A11ESE40F [DX1044#1]
N25Q032A11ESE40G [DX1044#1]
N25Q032A11ESF40F [DX1033#1]
N25Q032A11ESF40G [DX1033#1]
N25Q032A13E1240E [DX5157]
N25Q032A13E1240F [DX5157]
N25Q032A13E1241E [DX5157]
N25Q032A13E1241F [DX5157]
N25Q032A13EF440E [DX4081]
N25Q032A13EF440F [DX4081]
N25Q032A13EF640E [DX4005#1]
N25Q032A13EF640F [DX4005#1]
N25Q032A13EF840E [DX4005#1]
N25Q032A13EF840F [DX4005#1]
N25Q032A13ESC40F [DX1045#1]
N25Q032A13ESC40G [DX1045#1]
N25Q032A13ESCA0F [DX1045#1]
N25Q032A13ESE40F [DX1044#1]
N25Q032A13ESE40G [DX1044#1]
N25Q032A13ESE42ESE42EE01 [DX1044#1]
N25Q032A13ESEA0F [DX1044#1]
N25Q032A13ESEH0F [DX1044#1]
N25Q032A13ESF40F [DX1033#1]
N25Q032A13ESF40G [DX1033#1]
N25Q032A13ESFA0F [DX1033#1]
N25Q032A13ESFH0F [DX1033#1]
N25Q064A11EF640E [DX4006#1]
N25Q064A11EF640F [DX4006#1]
N25Q064A11ESE40F [DX1044#1]
N25Q064A11ESE40G [DX1044#1]
N25Q064A11ESF40F [DX1033#1]
N25Q064A11ESF40G [DX1033#1]
N25Q064A13E1240E [DX5157]
N25Q064A13E1240F [DX5157]
N25Q064A13E1241E [DX5157]
N25Q064A13E1241F [DX5157]
N25Q064A13E1247E [DX5157]
N25Q064A13E1247F [DX5157]
N25Q064A13EF640E [DX4006#1]
N25Q064A13EF640F [DX4006#1]
N25Q064A13EF840E [DX4006#1]
N25Q064A13EF840F [DX4006#1]
N25Q064A13EF8A0F [DX4006#1]
N25Q064A13EF8H0F [DX4006#1]
N25Q064A13ESE40E [DX1044#1]
N25Q064A13ESE40F [DX1044#1]
N25Q064A13ESE40G [DX1044#1]
N25Q064A13ESEH0F [DX1044#1]
N25Q064A13ESF40F [DX1033#1]
N25Q064A13ESF40G [DX1033#1]
N25Q064A13ESF41F [DX1033#1]
N25Q064A13ESF41G [DX1033#1]
N25Q064A13ESF42F [DX1033#1]
N25Q064A13ESF42G [DX1033#1]
N25Q064A13ESFA0F [DX1033#1]
N25Q064A13ESFH0E [DX1033#1]

N25Q064A13ESFH0F [DX1033#1]
N25Q128@BGA24 [DX5157]
N25Q128@MLP8 [DX4005#1]
N25Q128@SOIC16 [DX1072#1]
N25Q128@SOP8 [DX1044#1]
N25Q128@VDFPN8 [DX4006#1]
N25Q128A11B@BGA24 [DX5157]
N25Q128A11B@MLP8 [DX4005#1]
N25Q128A11B@SOIC16 [DX1072#1]
N25Q128A11B@SOP8 [DX1044#1]
N25Q128A11B@VDFPN8 [DX4006#1]
N25Q128A11E@BGA24 [DX5157]
N25Q128A11E@MLP8 [DX4005#1]
N25Q128A11E@SOIC16 [DX1072#1]
N25Q128A11E@SOP8 [DX1044#1]
N25Q128A11E@VDFPN8 [DX4006#1]
N25Q128A11T@BGA24 [DX5157]
N25Q128A11T@MLP8 [DX4005#1]
N25Q128A11T@SOIC16 [DX1072#1]
N25Q128A11T@SOP8 [DX1044#1]
N25Q128A11T@VDFPN8 [DX4006#1]
N25Q128A13B@BGA24 [DX5157]
N25Q128A13B@MLP8 [DX4005#1]
N25Q128A13B@SOIC16 [DX1072#1]
N25Q128A13B@SOP8 [DX1044#1]
N25Q128A13B@VDFPN8 [DX4006#1]
N25Q128A13E@BGA24 [DX5157]
N25Q128A13E@MLP8 [DX4005#1]
N25Q128A13E@SOIC16 [DX1072#1]
N25Q128A13E@SOP8 [DX1044#1]
N25Q128A13E@VDFPN8 [DX4006#1]
N25Q128A13T@BGA24 [DX5157]
N25Q128A13T@MLP8 [DX4005#1]
N25Q128A13T@SOIC16 [DX1072#1]
N25Q128A13T@SOP8 [DX1044#1]
N25Q128A13T@VDFPN8 [DX4006#1]
N25Q256A@BGA24 [DX5157]
N25Q256A@MLP8 [DX4005#1]
N25Q256A@SOIC16 [DX1072#1]
N25Q256A@SOP8 [DX1044#1]
N25Q256A@VDFPN8 [DX4006#1]
N25Q256A11E1240E [DX5157]
N25Q256A11E1240F [DX5157]
N25Q256A11E1241E [DX5157]
N25Q256A11E1241F [DX5157]
N25Q256A11EF840E [DX4006#1]
N25Q256A11EF840F [DX4006#1]
N25Q256A11ESF40F [DX1033#1]
N25Q256A11ESF40G [DX1033#1]
N25Q256A13E1240E [DX5157]
N25Q256A13E1240F [DX5157]
N25Q256A13E1241E [DX5157]
N25Q256A13E1241F [DX5157]
N25Q256A13EF840E [DX4006#1]
N25Q256A13EF840F [DX4006#1]
N25Q256A13ESF40F [DX1033#1]
N25Q256A13ESF40G [DX1033#1]
N25Q256A13ESFA0F [DX1033#1]
N25Q256A13ESFH0F [DX1033#1]
N25Q256A13Ex@BGA24 [DX5157]
N25Q256A13Ex@MLP8 [DX4005#1]
N25Q256A13Ex@SOIC16 [DX1072#1]
N25Q256A13Ex@SOP8 [DX1044#1]
N25Q256A13Ex@VDFPN8 [DX4006#1]
N25Q256A33E1241E [DX5157]
N25Q256A33E1241F [DX5157]
N25Q256A33EF840E [DX4006#1]
N25Q256A33EF840F [DX4006#1]
N25Q256A33ESF40F [DX1033#1]
N25Q256A33ESF40G [DX1033#1]
N25Q256A73ESF40F [DX1033#1]
N25Q256A73ESF40G [DX1033#1]
N25Q256A83E1240E [DX5157]
N25Q256A83E1240F [DX5157]
N25Q256A83E1241E [DX5157]
N25Q256A83E1241F [DX5157]
N25Q256A83ESF40 [DX1033#1]
N25Q256A83ESF40F [DX1033#1]
N25Q256A83ESF40G [DX1033#1]
N25Q512A11G1240E [DX5157]
N25Q512A11G1240F [DX5157]
N25Q512A11GSF40F [DX1033#1]
N25Q512A11GSF40G [DX1033#1]
N25Q512A13G1240E [DX5157]
N25Q512A13G1240F [DX5157]
N25Q512A13G1241E [DX5157]
N25Q512A13G1241F [DX5157]
N25Q512A13GF840E [DX4006#1]
N25Q512A13GF840F [DX4006#1]
N25Q512A13GSF40F [DX1033#1]
N25Q512A13GSF40G [DX1033#1]
N25Q512A83G1240E [DX5157]
N25Q512A83G1240F [DX5157]
N25Q512A83G1241E [DX5157]
N25Q512A83G1241F [DX5157]
N25Q512A83GSF40F [DX1033#1]

N25Q512A83GSF40G [DX1033#1]
N3L0219071F5620@FBGA64 [DX5066]
N3L0219081F5620@FBGA64 [DX5066]
N3L0219091F5620@FBGA64 [DX5066]
N3L0619091F5310E@FBGA132 [DX5069]
N3L0619091F5310F@FBGA132 [DX5069]
NP5Q032AE3ESFC0E [DX1033#1]
NP5Q064AE3ESFC0E [DX1033#1]
NP5Q128A13ESFC0E [DX1033#1]
NP5Q128AE3ESFC0E [DX1033#1]
NP8P128A13B@FBGA64 [DX5019]
NP8P128A13B@TSOP56 [DX1011]
NP8P128A13T@FBGA64 [DX5019]
NP8P128A13T@TSOP56 [DX1011]
PF58F0095HVT0B0 [DX5005]

MICRONAS

MICROCONTROLLER

SDA555XFL@SDIP52 [DX0056]

MICRON-CUSTOMER

E(E)PROM/FRAM/NVRAM

MT29C1G12MACNAJC(MBBM)@FBGA107 [DX5028]
MT29C1G12MACPAJC(MBBM)@FBGA107 [DX5028]
MT29C1G12MAUTAJA(XSR1.0)@FBGA137 [DX5011]
MT29C1G12MAVNAJC(XY)@FBGA107 [DX5028]
MT29C1G56MACEAJC(MBBM)@FBGA107 [DX5028]
MT29C1G56MACFAJC(MBBM)@FBGA107 [DX5028]
MT29C1G56MAUAAAJC(ICERA)@FBGA107 [DX5028]
MT29C1G56MAVAAAJ(ICERA)@FBGA107 [DX5028]
MT29C2G24MAKJAJC(M310)@FBGA107 [DX5028]
MT29C2G24MAKLAJA(MLT-XY)@FBGA137 [DX5011]
MT29C2G48MAKJCJC(FSK)@FBGA107 [DX5028]
MT29C2G48MAKJCJC(HUABAO)@FBGA107 [DX5028]
MT29C2G48MAKLCJA(MLT-DJ)@FBGA137 [DX5011]
MT29C4G48MAPLCJA(LEADCORE) [DX5011]
MT29F128G08CFAAAWP(LINKS)@TSOP48 [DX1004-1]
MT29F16G08CBACA(S3)@TSOP48 [DX1004-3]
MT29F1G08ABADAH4(ACCTON)@FBGA63 [DX5046]
MT29F1G08ABADAH4(ST273)@FBGA63 [DX5046-1]
MT29F1G08ABADAWP(CHUANGJ)@TSOP48 [DX1004-3]
MT29F1G08ABADAWP(Omron)@TSOP48 [DX1004-1]
MT29F1G08ABADAWP(ST7162)@TSOP48 [DX1004]
MT29F1G08ABAE(ST273)@TSOP48 [DX1004-3]
MT29F1G08ABAEA(MTK)@TSOP48 [DX1004-3]
MT29F1G08ABAEA(ST237)@TSOP48 [DX1004-3]
MT29F1G08ABAEAH4(STH237)@FBGA63 [DX5046-1]
MT29F1G08ABCHC(ORB)@FBGA63 [DX5028]

MT29F1G08ABCHC(ORB2)@FBGA63 [DX5028]
MT29F2G08AADWP(PICOCHIP)@TSOP48 [DX1004-1]
MT29F2G08ABAEA(ST273)@TSOP48 [DX1004-3]
MT29F2G08ABAEAWP(BANG)@TSOP48 [DX1004-1]
MT29F2G16ABAEAWP(ECC)@TSOP48 [DX1004-1]
MT29F32G08CBABAWP(intel)@TSOP48 [DX1004]
MT29F32G08CBACA(S3)@TSOP48 [DX1004-3]
MT29F32G08CBADA(S3)(2G)@TSOP48 [DX1004-3]
MT29F32G08QAAWP(Intel)@TSOP48 [DX1004-1]
MT29F4G08AACWC(VPI)@TSOP48 [DX1004-1]
MT29F4G08AACWC(YAMEI)@TSOP48 [DX1004-1]
MT29F4G08ABADAWP(BANG)@TSOP48 [DX1004-1]
MT29F4G08ABADAWP(NEW)@TSOP48 [DX1004-1]
MT29F4G08ABADAWP(VPI)@TSOP48 [DX1004-1]
MT29F4G16ABBDAH4(XY)@FBGA63 [DX5046]
MT29F64G08CBABB(2G)(S3)@TSOP48 [DX1004-3]
MT29F8G08ABABAWP(HI3716)@TSOP48 [DX1004-3]
MT29F8G16ADBDAH4(XY)@FBGA63 [DX5046]
MTFC16GKQDI(INTEL)(20M)@FBGA169 [DX5158]
MTFC16GKQDI(INTEL)@FBGA169 [DX5158]
MTFC2GGQDI(INTEL)(20M)@FBGA169 [DX5158]
MTFC2GGQDI(INTEL)@FBGA169 [DX5158]
MTFC2GGQDM(INTEL)(20M)@FBGA153 [DX5158]
MTFC2GGQDM(INTEL)@FBGA153 [DX5158]
MTFC32GKQDN(INTEL)(20M)@FBGA169 [DX5158]
MTFC32GKQDN(INTEL)@FBGA169 [DX5158]
MTFC4GGQDI(INTEL)(20M)@FBGA169 [DX5158]
MTFC4GGQDI(INTEL)@FBGA169 [DX5158]
MTFC4GGQDM(INTEL)(20M)@FBGA153 [DX5158]
MTFC4GGQDM(INTEL)@FBGA153 [DX5158]
MTFC8GKQDI(INTEL)(20M)@FBGA169 [DX5158]
MTFC8GKQDI(INTEL)@FBGA169 [DX5158]

MICROSEMI

E(E)PROM/FRAM/NVRAM

MS29C4G48MAZAKC1@BGA152 [DX5254]

MIP

E(E)PROM/FRAM/NVRAM

M71PL064B0@FBGA56 [DX5045]　　M71PL064B0@FBGA56(ZTE) [DX5005]

MIRA

E(E)PROM/FRAM/NVRAM

P1UAGA30AT@TSOP48 [DX1004-1]
PALA394AB@FBGA107 [DX5028]
PALA494AC@FBGA130 [DX5140-1]
PSU12A30BT@TSOP48 [DX1004-3]
PSU12S20BN@WSON8
PSU1G20BN@WSON8
PSU1GA30BT@TSOP48 [DX1004-3]
PSU1GA30HT@TSOP48 [DX1004-1]
PSU2GA30BT@TSOP48 [DX1004-3]
PSU4GA30AT@TSOP48 [DX1004-3]

MIRA-CUSTOMER

E(E)PROM/FRAM/NVRAM

PSU1GA30HT(DaXian)@TSOP48 [DX1004-1]

MITSUBISH

MICROCONTROLLER

R5F21346XJFP [DX3007]
R5F21346XKFP [DX3007]
R5F21347XJFP [DX3007]
R5F21347XKFP [DX3007]
R5F21348XJFP [DX3007]
R5F21348XKFP [DX3007]
R5F2134AXJFP [DX3007]
R5F2134AXKFP [DX3007]
R5F2134CXJFP [DX3007]
R5F2134CXKFP [DX3007]

MITSUBISHI

E(E)PROM/FRAM/NVRAM

M5L27128K [DX0001]
M5L2716 [DX0001]
M5L27256K [DX0001]
M5L2732 [DX0001]
M5L2732A [DX0001]
M5L27512 [DX0001]
M5L27512K [DX0001]
M5L2764K [DX0001]
M5L27C512A [DX0001]
M5M27128P [DX0001]
M5M27256P [DX0001]
M5M27512P [DX0001]
M5M2764P [DX0001]
M5M27C100K [DX0001]
M5M27C100K@PLCC32 [DX2032]
M5M27C100K@TSOP32 [DX1002]
M5M27C100P [DX0001]
M5M27C100P@PLCC32 [DX2032]
M5M27C100P@TSOP32 [DX1002]
M5M27C101JK [DX0001]
M5M27C101JK@PLCC32 [DX2032]
M5M27C101JK@TSOP32 [DX1002]
M5M27C101K [DX0001]
M5M27C101K@PLCC32 [DX2032]
M5M27C101K@TSOP32 [DX1002]
M5M27C101P [DX0001]
M5M27C101P@PLCC32 [DX2032]
M5M27C101P@TSOP32 [DX1002]
M5M27C102K [DX0001]
M5M27C102K@PLCC44 [DX2044]
M5M27C102P [DX0001]
M5M27C102P@PLCC44 [DX2044]

M5M27C128K [DX0001]
M5M27C201K [DX0001]
M5M27C201K@PLCC32 [DX2032]
M5M27C201K@TSOP32 [DX1002]
M5M27C202K [DX0001]
M5M27C202K@PLCC44 [DX2044]
M5M27C256(K) [DX0001]
M5M27C256(P) [DX0001]
M5M27C256A(FP) [DX0001]
M5M27C256A(K) [DX0001]
M5M27C256A(P) [DX0001]
M5M27C401K [DX0001]
M5M27C401K@PLCC32 [DX2032]
M5M27C401K@TSOP32 [DX1002]
M5M27C402K [DX0001]
M5M27C512(FP) [DX0001]
M5M27C512A(FP) [DX0001]
M5M27C512A(K) [DX0001]
M5M27C512A(P) [DX0001]
M5M28F101 [DX0001]
M5M28F101(REVERSE)@TSOP32 [DX1002]
M5M28F101@PLCC32 [DX2032]
M5M28F101@SOP32 [DX1019]
M5M28F101@TSOP32 [DX1002]
M5M28F101A [DX0001]
M5M28F101A(REVERSE)@TSOP32 [DX1002]
M5M28F101A@PLCC32 [DX2032]
M5M28F101A@SOIC32 [DX1019]
M5M28F101A@TSOP32 [DX1002]
M5M28FB800(VP)@TSOP48 [DX1043]
M5M28FT800(VP)@TSOP48 [DX1043]
M5M29FB160A@TSOP48 [DX1043]
M5M29FB800(FP)@PSOP44 [DX1014]
M5M29FB800(VP)@TSOP48 [DX1043]
M5M29FT160A@TSOP48 [DX1043]
M5M29FT800(FP)@PSOP44 [DX1014]
M5M29FT800(VP)@TSOP48 [DX1043]
M5M29GB160B(VP)@TSOP48 [DX1043]
M5M29GB320(VP)@TSOP48 [DX1043]
M5M29GB320(WG)@CBGA48 [DX50UN]
M5M29GB640VP@TSOP48 [DX1043]
M5M29GT160B(VP)@TSOP48 [DX1043]
M5M29GT320(VP)@TSOP48 [DX1043]
M5M29GT320(WG)@CBGA48 [DX50UN]
M5M29GT640VP@TSOP48 [DX1043]
M5M29JB160A@TSOP48 [DX1043]
M5M29JT160A@TSOP48 [DX1043]
M6M80011A [DX0001]
M6M80011A@SOIC10 [DX1032]
M6M80011A@SOIC16 [DX1032]
M6M80021 [DX0001]
M6M80021@SOIC10 [DX1032]
M6M80021@SOIC16 [DX1032]
M6M80041 [DX0001]
M6M80041@SOIC10 [DX1032]
M6MG3B641S16TP@TSOP52 [DX1009]
M6MG3T641S16TP@TSOP52 [DX1009]
M6MGB166S4B(WG)@FBGA72 [DX5001]
M6MGB321S4TP@TSOP52 [DX1009]
M6MGB321S8TP@TSOP52 [DX1009]
M6MGB32BS4WG@CSP66 [DX5001]
M6MGB32BS8WG@CSP66 [DX5001]
M6MGB331S8KT@TSOP52 [DX1009]
M6MGB33BS8AWG@CSP66 [DX5001]
M6MGB641S16TP@TSOP52 [DX1009]
M6MGB641S4TP@TSOP52 [DX1009]
M6MGB641S8TP@TSOP52 [DX1009]
M6MGB64BS4WG@CSP67 [DX5001]
M6MGB64BS8WG@CSP67 [DX5001]
M6MGD137W33(WG)@CSP72 [DX5053]
M6MGE157S4KT@TSOP52 [DX1009]
M6MGT166S4B(WG)@FBGA72 [DX5001]
M6MGT321S4TP@TSOP52 [DX1009]
M6MGT321S8TP@TSOP52 [DX1009]
M6MGT32BS4WG@CSP66 [DX5001]
M6MGT32BS8WG@CSP66 [DX5001]
M6MGT331S8KT@TSOP52 [DX1009]
M6MGT33BS8AWG@CSP66 [DX5001]
M6MGT641S16TP@TSOP52 [DX1009]
M6MGT641S4TP@TSOP52 [DX1009]
M6MGT641S8TP@TSOP52 [DX1009]
M6MGT64BS4WG@CSP67 [DX5001]
M6MGT64BS8WG@CSP67 [DX5001]

DRAM & SRAM

M5M51008BFP [DX1020]
M5M51008BP [DX0001]

M5M51008DFP [DX1020]
M5M51008DP [DX0001]

MICROCONTROLLER

M30260F3AGP@QFP48 [DX3007]
M30260F3TGP@QFP48 [DX3007]
M30260F3VGP@QFP48 [DX3007]
M30260F6AGP@QFP48 [DX3007]
M30260F6TGP@QFP48 [DX3007]
M30260F6VGP@QFP48 [DX3007]
M30260F8AGP@QFP48 [DX3007]
M30260F8TGP@QFP48 [DX3007]
M30260F8VGP@QFP48 [DX3007]
M30262F3GP@QFP48 [DX3007]
M30262F4GP@QFP48 [DX3007]
M30262F6GP@QFP48 [DX3007]
M30262F8GP@QFP48 [DX3007]
M30263F3AFP@SSOP42 [DX1056]
M30263F6AFP@SSOP42 [DX1056]
M30263F8AFP@SSOP42 [DX1056]
M30280F6HP@QFP80 [DX3016]
M30280F8HP@QFP80 [DX3016]
M30280FAHP@QFP80 [DX3016]
M30280FATHP@QFP80 [DX3016]
M30280FAVHP@QFP80 [DX3016]
M30280FCHP@QFP80 [DX3016]
M30281F6HP@QFP64 [DX3011]
M30281F8HP@QFP64 [DX3011]
M30281FAHP@QFP64 [DX3011]
M30281FATHP@QFP64 [DX3011]
M30281FAVHP@QFP64 [DX3011]
M30281FCHP@QFP64 [DX3011]
M30290FAHP@QFP80 [DX3016]
M30290FATHP@QFP80 [DX3016]
M30290FAVHP@QFP80 [DX3016]
M30290FCHP@QFP80 [DX3016]
M30290FCTHP@QFP80 [DX3016]
M30290FCVHP@QFP80 [DX3016]
M30291F8HP@QFP64 [DX3011]
M30291F8THP@QFP64 [DX3011]
M30291F8VHP@QFP64 [DX3011]
M30291FAHP@QFP64 [DX3011]
M30291FATHP@QFP64 [DX3011]
M30291FAVHP@QFP64 [DX3011]
M30291FCHP@QFP64 [DX3011]
M30291FCTHP@QFP64 [DX3011]
M30291FCVHP@QFP64 [DX3011]
M30302FAPFP@PQFP100 [DX3045]
M30302FAPGP@QFP100 [DX3021]
M30302FCPFP@PQFP100 [DX3045]
M30302FCPGP@QFP100 [DX3021]
M30302FEPFP@PQFP100 [DX3045]
M30302FEPGP@QFP100 [DX3021]
M3030RFAPFP [DX3045]
M3030RFAPGP [DX3021]
M3030RFCPFP [DX3045]
M3030RFCPGP [DX3021]
M3030RFEPFP [DX3045]
M3030RFEPGP [DX3021]
M3030RFGPFP [DX3045]
M3030RFGPGP [DX3021]
M30620FCAFP@PQFP100 [DX3045]
M30620FCAGP@TQFP100 [DX3021]
M30620FCNFP@PQFP100 [DX3045]
M30620FCNGP@TQFP100 [DX3021]
M30620FCPFP@PQFP100 [DX3045]
M30620FCPFP@PQFP100(S) [DX3045]
M30620FCPGP@TQFP100 [DX3021]
M30620FCPGP@TQFP100(S) [DX3021]
M30621FCPGP@TQFP100(S) [DX3018]
M30622F8PFP@PQFP100 [DX3045]
M30622F8PFP@PQFP100(S) [DX3045]
M30622F8PGP@TQFP100 [DX3021]
M30622F8PGP@TQFP100(S) [DX3021]
M30624FGAFP@PQFP100 [DX3045]
M30624FGAGP@TQFP100 [DX3021]
M30624FGMFP@PQFP100 [DX3045]
M30624FGMGP@TQFP100 [DX3021]
M30624FGNFP@PQFP100 [DX3045]
M30624FGNGP@TQFP100 [DX3021]
M30624FGPFP@PQFP100 [DX3045]
M30624FGPFP@PQFP100(S) [DX3045]
M30624FGPGP@TQFP100 [DX3021]
M30624FGPGP@TQFP100(S) [DX3021]
M30625FGPGP@TQFP128 [DX3032]
M30625FGPGP@TQFP128(S) [DX3032]
M30626FHPFP@PQFP100 [DX3045]
M30626FHPFP@PQFP100(S) [DX3045]
M30626FHPGP@TQFP100 [DX3021]
M30626FHPGP@TQFP100(S) [DX3021]

M30626FJPFP@PQFP100 [DX3045]
M30626FJPGP@PQFP100 [DX3021]
M30627FHPGP@PQFP128 [DX3032]
M30627FJPGP@PQFP128 [DX3032]
M3062AFCTFP@PQFP100 [DX3045]
M3062AFCTGP@PQFP100 [DX3021]
M3062AFCVFP@PQFP100 [DX3045]
M3062AFCVGP@PQFP100 [DX3021]
M3062CF8TFP@PQFP100 [DX3045]
M3062CF8TGP@PQFP100 [DX3021]
M3062JFHTFP@PQFP100 [DX3045]
M3062JFHTGP@PQFP100 [DX3021]
M3062JFHVFP@PQFP100 [DX3045]
M3062JFHVGP@PQFP100 [DX3021]
M3062LFGPFP@PQFP100 [DX3045]
M3062LFGPGP@TQFP100 [DX3021]
M306N4FCFP@PQFP100 [DX3045]
M306N4FCTFP@PQFP100 [DX3045]
M306N4FCVFP@PQFP100 [DX3045]
M306N4FGFP@PQFP100 [DX3045]
M306N4FGTFP@PQFP100 [DX3045]
M306N4FGVFP@PQFP100 [DX3045]
M306N5FCFP@PQFP100 [DX3045]
M306N5FCTFP@PQFP100 [DX3045]
M306N5FCVFP@PQFP100 [DX3045]
M306NAFGTFP@PQFP100 [DX3045]
M306NKFHGP@QFP100 [DX3021]
M306NKFHVGP@QFP100 [DX3021]
M306NKFJTGP@QFP100 [DX3021]
M306NLFHGP@QFP100 [DX3021]
M306NLFHVGP@QFP100 [DX3021]
M306NLFJTGP@QFP100 [DX3021]
M306NMFHGP@QFP128 [DX3032]
M306NMFHVGP@QFP128 [DX3032]
M306NMFJTGP@QFP128 [DX3032]
M306NNFHGP@QFP128 [DX3032]
M306NNFHVGP@QFP128 [DX3032]
M306NNFJTGP@QFP128 [DX3032]
M30833FJFP@PQFP100 [DX3045]
M30833FJTGP@TQFP100 [DX3021]
M30873FHGP@TQFP100 [DX3021]
M30876FJGP@TQFP100 [DX3021]
M30879FKGP@TQFP100 [DX3021]
M30879FLGP@TQFP100 [DX3021]
M3087BFLGP@TQFP144 [DX3035]
M34283G2GP [DX1067]
M34508G4FP [DX1031]
M34508G4HFP [DX1031]
M30626FJPFP@PQFP100(S) [DX3045]
M30626FJPGP@PQFP100(S) [DX3021]
M30627FHPGP@PQFP128(S) [DX3032]
M30627FJPGP@PQFP128(S) [DX3032]
M3062AFCTFP@PQFP100(S) [DX3045]
M3062AFCTGP@PQFP100(S) [DX3021]
M3062AFCVFP@PQFP100(S) [DX3045]
M3062AFCVGP@PQFP100(S) [DX3021]
M3062CF8TFP@PQFP100(S) [DX3045]
M3062CF8TGP@PQFP100(S) [DX3021]
M3062JFHTFP@PQFP100(S) [DX3045]
M3062JFHTGP@PQFP100(S) [DX3021]
M3062JFHVFP@PQFP100(S) [DX3045]
M3062JFHVGP@PQFP100(S) [DX3021]
M3062LFGPFP@PQFP100(S) [DX3045]
M3062LFGPGP@TQFP100(S) [DX3021]
M306N4FCGP@QFP100 [DX3021]
M306N4FCTGP@QFP100 [DX3021]
M306N4FCVGP@QFP100 [DX3021]
M306N4FGGP@QFP100 [DX3021]
M306N4FGTGP@QFP100 [DX3021]
M306N4FGVGP@QFP100 [DX3021]
M306N5FCGP@QFP100 [DX3021]
M306N5FCTGP@QFP100 [DX3021]
M306N5FCVGP@QFP100 [DX3021]
M306NBFCTFP@PQFP100 [DX3045]
M306NKFHTGP@QFP100 [DX3021]
M306NKFJGP@QFP100 [DX3021]
M306NKFJVGP@QFP100 [DX3021]
M306NLFHTGP@QFP100 [DX3021]
M306NLFJGP@QFP100 [DX3021]
M306NLFJVGP@QFP100 [DX3021]
M306NMFHTGP@QFP128 [DX3032]
M306NMFJGP@QFP128 [DX3032]
M306NMFJVGP@QFP128 [DX3032]
M306NNFHTGP@QFP128 [DX3032]
M306NNFJGP@QFP128 [DX3032]
M306NNFJVGP@QFP128 [DX3032]
M30833FJGP@TQFP100 [DX3021]
M30835FJGP@QFP144 [DX3035]
M30875FHGP@TQFP144 [DX3035]
M30878FJGP@TQFP144 [DX3035]
M30879FLFP@TQFP100 [DX3045]
M3087BFKGP@TQFP144 [DX3035]
M34282E2GP [DX1000]
M34286G2GP [DX1067]
M34508G4GP [DX1067]
M34508G4HGP [DX1067]

M34509G4FP [DX1047]
M34509G4HFP [DX1047]
M34559G6FP@QFP52 [DX3010]
M3455AG8FP@QFP52 [DX3010]
M3455AGCFP@QFP52 [DX3010]
M37531E4FP@SSOP36 [DX1056]
M37531E8FP@SSOP36 [DX1056]
M37544G2(GP)@LQFP32 [DX3001]
M37544G2(SP)@SDIP32 [DX0032]
M37544G2A(GP)@LQFP32 [DX3001]
M37544G2A(SP)@SDIP32 [DX0032]
M37545G4(FP)@SSOP36 [DX1046]
M37545G4(GP)@LQFP32 [DX3001]
M37545G6(FP)@SSOP36 [DX1046]
M37545G6(GP)@LQFP32 [DX3001]
M37545G8(FP)@SSOP36 [DX1046]
M37545G8(GP)@LQFP32 [DX3001]
M37546G2(FP)@SSOP36 [DX1046]
M37546G2(GP)@LQFP32 [DX3001]
M37546G2(SP)@SDIP32 [DX0032]
M37546G4(FP)@SSOP36 [DX1046]
M37546G4(GP)@LQFP32 [DX3001]
M37546G4(SP)@SDIP32 [DX0032]
M37547G2(FP)@SSOP36 [DX1046]
M37547G4(FP)@SSOP36 [DX1046]
M37548G1(FP)@TSSOP20 [DX1000]
M37548G2(FP)@TSSOP20 [DX1000]
M37548G3(FP)@TSSOP20 [DX1000]
M37549G1FP@SSOP24 [DX1047]
M37549G1SP@SDIP24 [DX0032]
M37549G2FP@SSOP24 [DX1047]
M37549G2SP@SDIP24 [DX0032]
M37549G3FP@SSOP24 [DX1047]
M37549G3SP@SDIP24 [DX0032]
M38039FFFP@QFP64 [DX3044]
M38039FFHFP@QFP64 [DX3044]
M38039FFHHP@QFP64 [DX3011]
M38039FFHKP@QFP64 [DX3044]
M38039FFHP@QFP64 [DX3011]
M38039FFHSP@SDIP64 [DX0064]
M38039FFSP@SDIP64 [DX0064]
M38039G4HHP@QFP64 [DX3011]
M38039G4HKP@QFP64 [DX3013]
M38039G4HSP@SDIP64 [DX0064]
M38039G6HHP@QFP64 [DX3011]
M38039G6HKP@QFP64 [DX3013]
M38039G6HSP@SDIP64 [DX0064]
M38039G8HHP@QFP64 [DX3011]
M38039G8HKP@QFP64 [DX3013]
M38039G8HSP@SDIP64 [DX0064]
M38039GCHHP@QFP64 [DX3011]
M38039GCHKP@QFP64 [DX3013]
M38039GCHSP@SDIP64 [DX0064]
M38049FFFP@QFP64 [DX3044]
M38049FFHP@QFP64 [DX3011]
M38049FFSP@SDIP64 [DX0064]
M38234G4(FP)@PQFP80 [DX3020]
M38234G4(HP)@TQFP80 [DX3016]
M38235G6(FP)@PQFP80 [DX3020]
M38235G6(HP)@TQFP80 [DX3016]
M38238G8(FP)@PQFP80 [DX3020]
M38238G8(HP)@TQFP80 [DX3016]
M38239GC(FP)@PQFP80 [DX3020]
M38239GC(HP)@TQFP80 [DX3016]
M3823AGF(FP)@PQFP80 [DX3020]
M3823AGF(HP)@TQFP80 [DX3016]
M38503G4A(FP)@SSOP42 [DX1046]
M38503G4A(SP)@SDIP42 [DX0042]
M38507F8FP@SSOP42 [DX1056]
M38507F8SP@SDIP42 [DX0042]
M38588G6(FP)@SSOP42 [DX1046]
M38588G6(SP)@SDIP42 [DX0042]
M38588G8(FP)@SSOP42 [DX1046]
M38588G8(SP)@SDIP42 [DX0042]
M38588GC(FP)@SSOP42 [DX1046]
M38588GC(SP)@SDIP42 [DX0042]
M38859FFHP@QFP80 [DX3016]
M38D24G4(FP)@QFP64 [DX3013]
M38D24G4(HP)@QFP64 [DX3011]
M38D24G6(FP)@QFP64 [DX3013]
M38D24G6(HP)@QFP64 [DX3011]
M38D28G8(FP)@QFP64 [DX3013]
M38D28G8(HP)@QFP64 [DX3011]
M38D29FF(HP)@QFP64 [DX3011]
M38D29GC(FP)@QFP64 [DX3013]
M38D29GC(HP)@QFP64 [DX3011]
M38D29GF(FP)@QFP64 [DX3013]
M38D29GF(HP)@QFP64 [DX3011]
M38D58G8FP@PQFP80 [DX3020]
M38D58G8HP@QFP80 [DX3016]
M38D59FFFP@PQFP80 [DX3020]
M38D59FFHP@QFP80 [DX3016]
M38D59GCFP@PQFP80 [DX3020]
M38D59GCHP@QFP80 [DX3016]
M38D59GFFP@PQFP80 [DX3020]
M38D59GFHP@QFP80 [DX3016]

M3NN00FETGP@QFP100 [DX3021]
M3NN00FETGP@QFP100(S) [DX3021]
R5F21102DFP@TQFP32 [DX3001]
R5F21102FP@TQFP32 [DX3001]
R5F21103DFP@TQFP32 [DX3001]
R5F21103FP@TQFP32 [DX3001]
R5F21104DFP@TQFP32 [DX3001]
R5F21104FP@TQFP32 [DX3001]
R5F21112DFP@TQFP32 [DX3001]
R5F21112FP@TQFP32 [DX3001]
R5F21113DFP@TQFP32 [DX3001]
R5F21113FP@TQFP32 [DX3001]
R5F21114DFP@TQFP32 [DX3001]
R5F21114FP@TQFP32 [DX3001]
R5F21122DFP@TQFP32 [DX3001]
R5F21122FP@TQFP32 [DX3001]
R5F21123DFP@TQFP32 [DX3001]
R5F21123FP@TQFP32 [DX3001]
R5F21124DFP@TQFP32 [DX3001]
R5F21124FP@TQFP32 [DX3001]
R5F21132DFP@TQFP32 [DX3001]
R5F21132FP@TQFP32 [DX3001]
R5F21133DFP@TQFP32 [DX3001]
R5F21133FP@TQFP32 [DX3001]
R5F21134DFP@TQFP32 [DX3001]
R5F21134FP@TQFP32 [DX3001]
R5F21142DSP@TSSOP20 [DX1000]
R5F21142DSP@TSSOP20(single ISP) [DX0001]
R5F21142DSP@TSSOP20(single wire) [DX1000]
R5F21142DSP@TSSOP20(UART ISP) [DX0001]
R5F21142DSP@TSSOP20(UART mode) [DX1000]
R5F21142SP@TSSOP20 [DX1000]
R5F21142SP@TSSOP20(single ISP) [DX0001]
R5F21142SP@TSSOP20(single wire) [DX1000]
R5F21142SP@TSSOP20(UART ISP) [DX0001]
R5F21142SP@TSSOP20(UART mode) [DX1000]
R5F21143DSP@TSSOP20 [DX1000]
R5F21143DSP@TSSOP20(single ISP) [DX0001]
R5F21143DSP@TSSOP20(single wire) [DX1000]
R5F21143DSP@TSSOP20(UART ISP) [DX0001]
R5F21143DSP@TSSOP20(UART mode) [DX1000]
R5F21143SP@TSSOP20 [DX1000]
R5F21143SP@TSSOP20(single ISP) [DX0001]
R5F21143SP@TSSOP20(single wire) [DX1000]
R5F21143SP@TSSOP20(UART ISP) [DX0001]
R5F21143SP@TSSOP20(UART mode) [DX1000]
R5F21144DSP@TSSOP20 [DX1000]
R5F21144DSP@TSSOP20(single ISP) [DX0001]
R5F21144DSP@TSSOP20(single wire) [DX1000]
R5F21144DSP@TSSOP20(UART ISP) [DX0001]
R5F21144DSP@TSSOP20(UART mode) [DX1000]
R5F21144SP@TSSOP20 [DX1000]
R5F21144SP@TSSOP20(single ISP) [DX0001]
R5F21144SP@TSSOP20(single wire) [DX1000]
R5F21144SP@TSSOP20(UART ISP) [DX0001]
R5F21144SP@TSSOP20(UART mode) [DX1000]
R5F21152DSP@TSSOP20 [DX1000]
R5F21152DSP@TSSOP20(single ISP) [DX0001]
R5F21152DSP@TSSOP20(single wire) [DX1000]
R5F21152DSP@TSSOP20(UART ISP) [DX0001]
R5F21152DSP@TSSOP20(UART mode) [DX1000]

R5F21152SP@TSSOP20 [DX1000]
R5F21152SP@TSSOP20(single ISP) [DX0001]
R5F21152SP@TSSOP20(single wire) [DX1000]
R5F21152SP@TSSOP20(UART ISP) [DX0001]
R5F21152SP@TSSOP20(UART mode) [DX1000]
R5F21153DSP@TSSOP20 [DX1000]
R5F21153DSP@TSSOP20(single ISP) [DX0001]
R5F21153DSP@TSSOP20(single wire) [DX1000]
R5F21153DSP@TSSOP20(UART ISP) [DX0001]
R5F21153DSP@TSSOP20(UART mode) [DX1000]
R5F21153SP@TSSOP20 [DX1000]
R5F21153SP@TSSOP20(single ISP) [DX0001]
R5F21153SP@TSSOP20(single wire) [DX1000]
R5F21153SP@TSSOP20(UART ISP) [DX0001]
R5F21153SP@TSSOP20(UART mode) [DX1000]
R5F21154DSP@TSSOP20 [DX1000]
R5F21154DSP@TSSOP20(single ISP) [DX0001]
R5F21154DSP@TSSOP20(single wire) [DX1000]
R5F21154DSP@TSSOP20(UART ISP) [DX0001]
R5F21154DSP@TSSOP20(UART mode) [DX1000]
R5F21154SP@TSSOP20 [DX1000]
R5F21154SP@TSSOP20(single ISP) [DX0001]
R5F21154SP@TSSOP20(single wire) [DX1000]
R5F21154SP@TSSOP20(UART ISP) [DX0001]
R5F21154SP@TSSOP20(UART mode) [DX1000]
R5F21162DSP@TSSOP20 [DX1000]
R5F21162DSP@TSSOP20(single ISP) [DX0001]
R5F21162DSP@TSSOP20(single wire) [DX1000]
R5F21162DSP@TSSOP20(UART ISP) [DX0001]
R5F21162DSP@TSSOP20(UART mode) [DX1000]
R5F21162SP@TSSOP20 [DX1000]
R5F21162SP@TSSOP20(single ISP) [DX0001]
R5F21162SP@TSSOP20(single wire) [DX1000]
R5F21162SP@TSSOP20(UART ISP) [DX0001]
R5F21162SP@TSSOP20(UART mode) [DX1000]
R5F21163DSP@TSSOP20 [DX1000]
R5F21163DSP@TSSOP20(single ISP) [DX0001]
R5F21163DSP@TSSOP20(single wire) [DX1000]
R5F21163DSP@TSSOP20(UART ISP) [DX0001]
R5F21163DSP@TSSOP20(UART mode) [DX1000]
R5F21163SP@TSSOP20 [DX1000]
R5F21163SP@TSSOP20(single ISP) [DX0001]
R5F21163SP@TSSOP20(single wire) [DX1000]
R5F21163SP@TSSOP20(UART ISP) [DX0001]
R5F21163SP@TSSOP20(UART mode) [DX1000]
R5F21164DSP@TSSOP20 [DX1000]
R5F21164DSP@TSSOP20(single ISP) [DX0001]
R5F21164DSP@TSSOP20(single wire) [DX1000]

R5F21164DSP@TSSOP20(UART ISP) [DX0001]
R5F21164DSP@TSSOP20(UART mode) [DX1000]
R5F21164SP@TSSOP20 [DX1000]
R5F21164SP@TSSOP20(single ISP) [DX0001]
R5F21164SP@TSSOP20(single wire) [DX1000]
R5F21164SP@TSSOP20(UART ISP) [DX0001]
R5F21164SP@TSSOP20(UART mode) [DX1000]
R5F21172DSP@TSSOP20 [DX1000]
R5F21172DSP@TSSOP20(single ISP) [DX0001]
R5F21172DSP@TSSOP20(single wire) [DX1000]
R5F21172DSP@TSSOP20(UART ISP) [DX0001]
R5F21172DSP@TSSOP20(UART mode) [DX1000]
R5F21172SP@TSSOP20 [DX1000]
R5F21172SP@TSSOP20(single ISP) [DX0001]
R5F21172SP@TSSOP20(single wire) [DX1000]
R5F21172SP@TSSOP20(UART ISP) [DX0001]
R5F21172SP@TSSOP20(UART mode) [DX1000]
R5F21173DSP@TSSOP20 [DX1000]
R5F21173DSP@TSSOP20(single ISP) [DX0001]
R5F21173DSP@TSSOP20(single wire) [DX1000]
R5F21173DSP@TSSOP20(UART ISP) [DX0001]
R5F21173DSP@TSSOP20(UART mode) [DX1000]
R5F21173SP@TSSOP20 [DX1000]
R5F21173SP@TSSOP20(single ISP) [DX0001]
R5F21173SP@TSSOP20(single wire) [DX1000]
R5F21173SP@TSSOP20(UART ISP) [DX0001]
R5F21173SP@TSSOP20(UART mode) [DX1000]
R5F21174DSP@TSSOP20 [DX1000]
R5F21174DSP@TSSOP20(single ISP) [DX0001]
R5F21174DSP@TSSOP20(single wire) [DX1000]
R5F21174DSP@TSSOP20(UART ISP) [DX0001]
R5F21174DSP@TSSOP20(UART mode) [DX1000]
R5F21174SP@TSSOP20 [DX1000]
R5F21174SP@TSSOP20(single ISP) [DX0001]
R5F21174SP@TSSOP20(single wire) [DX1000]
R5F21174SP@TSSOP20(UART ISP) [DX0001]
R5F21174SP@TSSOP20(UART mode) [DX1000]
R5F21181DD@SDIP20 [DX0032]
R5F21181DD@SDIP20(single ISP) [DX0001]
R5F21181DD@SDIP20(single wire) [DX0032]
R5F21181DD@SDIP20(UART ISP) [DX0001]
R5F21181DD@SDIP20(UART mode) [DX0032]
R5F21181DSP@TSSOP20 [DX1000]
R5F21181DSP@TSSOP20(single ISP) [DX0001]
R5F21181DSP@TSSOP20(single wire) [DX1000]
R5F21181DSP@TSSOP20(UART ISP) [DX0001]
R5F21181DSP@TSSOP20(UART mode) [DX1000]
R5F21181SP@TSSOP20 [DX1000]

R5F21181SP@TSSOP20(single ISP) [DX0001]
R5F21181SP@TSSOP20(single wire) [DX1000]
R5F21181SP@TSSOP20(UART ISP) [DX0001]
R5F21181SP@TSSOP20(UART mode) [DX1000]
R5F21182DD@SDIP20 [DX0032]
R5F21182DD@SDIP20(single ISP) [DX0001]
R5F21182DD@SDIP20(single wire) [DX0032]
R5F21182DD@SDIP20(UART ISP) [DX0001]
R5F21182DD@SDIP20(UART mode) [DX0032]
R5F21182DSP@TSSOP20 [DX1000]
R5F21182DSP@TSSOP20(single ISP) [DX0001]
R5F21182DSP@TSSOP20(single wire) [DX1000]
R5F21182DSP@TSSOP20(UART ISP) [DX0001]
R5F21182DSP@TSSOP20(UART mode) [DX1000]
R5F21182NP@QFN28 [DX4013]
R5F21182NP@QFN28(single ISP) [DX0001]
R5F21182NP@QFN28(single wire) [DX4013]
R5F21182NP@QFN28(UART ISP) [DX0001]
R5F21182NP@QFN28(UART mode) [DX4013]
R5F21182SP@TSSOP20 [DX1000]
R5F21182SP@TSSOP20(single ISP) [DX0001]
R5F21182SP@TSSOP20(single wire) [DX1000]
R5F21182SP@TSSOP20(UART ISP) [DX0001]
R5F21182SP@TSSOP20(UART mode) [DX1000]
R5F21183DD@SDIP20 [DX0032]
R5F21183DD@SDIP20(single ISP) [DX0001]
R5F21183DD@SDIP20(single wire) [DX0032]
R5F21183DD@SDIP20(UART ISP) [DX0001]
R5F21183DD@SDIP20(UART mode) [DX0032]
R5F21183DSP@TSSOP20 [DX1000]
R5F21183DSP@TSSOP20(single ISP) [DX0001]
R5F21183DSP@TSSOP20(single wire) [DX1000]
R5F21183DSP@TSSOP20(UART ISP) [DX0001]
R5F21183DSP@TSSOP20(UART mode) [DX1000]
R5F21183NP@QFN28 [DX4013]
R5F21183NP@QFN28(single ISP) [DX0001]
R5F21183NP@QFN28(single wire) [DX4013]
R5F21183NP@QFN28(UART ISP) [DX0001]
R5F21183NP@QFN28(UART mode) [DX4013]
R5F21183SP@TSSOP20 [DX1000]
R5F21183SP@TSSOP20(single ISP) [DX0001]
R5F21183SP@TSSOP20(single wire) [DX1000]
R5F21183SP@TSSOP20(UART ISP) [DX0001]
R5F21183SP@TSSOP20(UART mode) [DX1000]
R5F21184DD@SDIP20 [DX0032]
R5F21184DD@SDIP20(single ISP) [DX0001]
R5F21184DD@SDIP20(single wire) [DX0032]
R5F21184DD@SDIP20(UART ISP) [DX0001]

R5F21184DD@SDIP20(UART mode) [DX0032]
R5F21184DSP@TSSOP20 [DX1000]
R5F21184DSP@TSSOP20(single ISP) [DX0001]
R5F21184DSP@TSSOP20(single wire) [DX1000]
R5F21184DSP@TSSOP20(UART ISP) [DX0001]
R5F21184DSP@TSSOP20(UART mode) [DX1000]
R5F21184NP@QFN28 [DX4013]
R5F21184NP@QFN28(single ISP) [DX0001]
R5F21184NP@QFN28(single wire) [DX4013]
R5F21184NP@QFN28(UART ISP) [DX0001]
R5F21184NP@QFN28(UART mode) [DX4013]
R5F21184SP@TSSOP20 [DX1000]
R5F21184SP@TSSOP20(single ISP) [DX0001]
R5F21184SP@TSSOP20(single wire) [DX1000]
R5F21184SP@TSSOP20(UART ISP) [DX0001]
R5F21184SP@TSSOP20(UART mode) [DX1000]
R5F21191DD@SDIP20 [DX0032]
R5F21191DD@SDIP20(single ISP) [DX0001]
R5F21191DD@SDIP20(single wire) [DX0032]
R5F21191DD@SDIP20(UART ISP) [DX0001]
R5F21191DD@SDIP20(UART mode) [DX0032]
R5F21191DSP@TSSOP20 [DX1000]
R5F21191DSP@TSSOP20(single ISP) [DX0001]
R5F21191DSP@TSSOP20(single wire) [DX1000]
R5F21191DSP@TSSOP20(UART ISP) [DX0001]
R5F21191DSP@TSSOP20(UART mode) [DX1000]
R5F21191SP@TSSOP20 [DX1000]
R5F21191SP@TSSOP20(single ISP) [DX0001]
R5F21191SP@TSSOP20(single wire) [DX1000]
R5F21191SP@TSSOP20(UART ISP) [DX0001]
R5F21191SP@TSSOP20(UART mode) [DX1000]
R5F21192DD@SDIP20 [DX0032]
R5F21192DD@SDIP20(single ISP) [DX0001]
R5F21192DD@SDIP20(single wire) [DX0032]
R5F21192DD@SDIP20(UART ISP) [DX0001]
R5F21192DD@SDIP20(UART mode) [DX0032]
R5F21192DSP@TSSOP20 [DX1000]
R5F21192DSP@TSSOP20(single ISP) [DX0001]
R5F21192DSP@TSSOP20(single wire) [DX1000]
R5F21192DSP@TSSOP20(UART ISP) [DX0001]
R5F21192DSP@TSSOP20(UART mode) [DX1000]
R5F21192NP@QFN28 [DX4013]
R5F21192NP@QFN28(single ISP) [DX0001]
R5F21192NP@QFN28(single wire) [DX4013]
R5F21192NP@QFN28(UART ISP) [DX0001]
R5F21192NP@QFN28(UART mode) [DX4013]
R5F21192SP@TSSOP20 [DX1000]
R5F21192SP@TSSOP20(single ISP) [DX0001]

R5F21192SP@TSSOP20(single wire) [DX1000]
R5F21192SP@TSSOP20(UART ISP) [DX0001]
R5F21192SP@TSSOP20(UART mode) [DX1000]
R5F21193DD@SDIP20 [DX0032]
R5F21193DD@SDIP20(single ISP) [DX0001]
R5F21193DD@SDIP20(single wire) [DX0032]
R5F21193DD@SDIP20(UART ISP) [DX0001]
R5F21193DD@SDIP20(UART mode) [DX0032]
R5F21193DSP@TSSOP20 [DX1000]
R5F21193DSP@TSSOP20(single ISP) [DX0001]
R5F21193DSP@TSSOP20(single wire) [DX1000]
R5F21193DSP@TSSOP20(UART ISP) [DX0001]
R5F21193DSP@TSSOP20(UART mode) [DX1000]
R5F21193NP@QFN28 [DX4013]
R5F21193NP@QFN28(single ISP) [DX0001]
R5F21193NP@QFN28(single wire) [DX4013]
R5F21193NP@QFN28(UART ISP) [DX0001]
R5F21193NP@QFN28(UART mode) [DX4013]
R5F21193SP@TSSOP20 [DX1000]
R5F21193SP@TSSOP20(single ISP) [DX0001]
R5F21193SP@TSSOP20(single wire) [DX1000]
R5F21193SP@TSSOP20(UART ISP) [DX0001]
R5F21193SP@TSSOP20(UART mode) [DX1000]
R5F21194DD@SDIP20 [DX0032]
R5F21194DD@SDIP20(single ISP) [DX0001]
R5F21194DD@SDIP20(single wire) [DX0032]
R5F21194DD@SDIP20(UART ISP) [DX0001]
R5F21194DD@SDIP20(UART mode) [DX0032]
R5F21194DSP@TSSOP20 [DX1000]
R5F21194DSP@TSSOP20(single ISP) [DX0001]
R5F21194DSP@TSSOP20(single wire) [DX1000]
R5F21194DSP@TSSOP20(UART ISP) [DX0001]
R5F21194DSP@TSSOP20(UART mode) [DX1000]
R5F21194NP@QFN28 [DX4013]
R5F21194NP@QFN28(single ISP) [DX0001]
R5F21194NP@QFN28(single wire) [DX4013]
R5F21194NP@QFN28(UART ISP) [DX0001]
R5F21194NP@QFN28(UART mode) [DX4013]
R5F21194SP@TSSOP20 [DX1000]
R5F21194SP@TSSOP20(single ISP) [DX0001]
R5F21194SP@TSSOP20(single wire) [DX1000]
R5F21194SP@TSSOP20(UART ISP) [DX0001]
R5F21194SP@TSSOP20(UART mode) [DX1000]
R5F211A1DD@SDIP20 [DX0032]
R5F211A1DD@SDIP20(single ISP) [DX0001]
R5F211A1DD@SDIP20(single wire) [DX0032]
R5F211A1DD@SDIP20(UART ISP) [DX0001]
R5F211A1DD@SDIP20(UART mode) [DX0032]

R5F211A1DSP@TSSOP20 [DX1000]
R5F211A1DSP@TSSOP20(single ISP) [DX0001]
R5F211A1DSP@TSSOP20(single wire) [DX1000]
R5F211A1DSP@TSSOP20(UART ISP) [DX0001]
R5F211A1DSP@TSSOP20(UART mode) [DX1000]
R5F211A1SP@TSSOP20 [DX1000]
R5F211A1SP@TSSOP20(single ISP) [DX0001]
R5F211A1SP@TSSOP20(single wire) [DX1000]
R5F211A1SP@TSSOP20(UART ISP) [DX0001]
R5F211A1SP@TSSOP20(UART mode) [DX1000]
R5F211A2DD@SDIP20 [DX0032]
R5F211A2DD@SDIP20(single ISP) [DX0001]
R5F211A2DD@SDIP20(single wire) [DX0032]
R5F211A2DD@SDIP20(UART ISP) [DX0001]
R5F211A2DD@SDIP20(UART mode) [DX0032]
R5F211A2DSP@TSSOP20 [DX1000]
R5F211A2DSP@TSSOP20(single ISP) [DX0001]
R5F211A2DSP@TSSOP20(single wire) [DX1000]
R5F211A2DSP@TSSOP20(UART ISP) [DX0001]
R5F211A2DSP@TSSOP20(UART mode) [DX1000]
R5F211A2NP@QFN28 [DX4013]
R5F211A2NP@QFN28(single ISP) [DX0001]
R5F211A2NP@QFN28(single wire) [DX4013]
R5F211A2NP@QFN28(UART ISP) [DX0001]
R5F211A2NP@QFN28(UART mode) [DX4013]
R5F211A2SP@TSSOP20 [DX1000]
R5F211A2SP@TSSOP20(single ISP) [DX0001]
R5F211A2SP@TSSOP20(single wire) [DX1000]
R5F211A2SP@TSSOP20(UART ISP) [DX0001]
R5F211A2SP@TSSOP20(UART mode) [DX1000]
R5F211A3DD@SDIP20 [DX0032]
R5F211A3DD@SDIP20(single ISP) [DX0001]
R5F211A3DD@SDIP20(single wire) [DX0032]
R5F211A3DD@SDIP20(UART ISP) [DX0001]
R5F211A3DD@SDIP20(UART mode) [DX0032]
R5F211A3DSP@TSSOP20 [DX1000]
R5F211A3DSP@TSSOP20(single ISP) [DX0001]
R5F211A3DSP@TSSOP20(single wire) [DX1000]
R5F211A3DSP@TSSOP20(UART ISP) [DX0001]
R5F211A3DSP@TSSOP20(UART mode) [DX1000]
R5F211A3NP@QFN28 [DX4013]
R5F211A3NP@QFN28(single ISP) [DX0001]
R5F211A3NP@QFN28(single wire) [DX4013]
R5F211A3NP@QFN28(UART ISP) [DX0001]
R5F211A3NP@QFN28(UART mode) [DX4013]
R5F211A3SP@TSSOP20 [DX1000]
R5F211A3SP@TSSOP20(single ISP) [DX0001]
R5F211A3SP@TSSOP20(single wire) [DX1000]

R5F211A3SP@TSSOP20(UART ISP) [DX0001]
R5F211A3SP@TSSOP20(UART mode) [DX1000]
R5F211A4DD@SDIP20 [DX0032]
R5F211A4DD@SDIP20(single ISP) [DX0001]
R5F211A4DD@SDIP20(single wire) [DX0032]
R5F211A4DD@SDIP20(UART ISP) [DX0001]
R5F211A4DD@SDIP20(UART mode) [DX0032]
R5F211A4DSP@TSSOP20 [DX1000]
R5F211A4DSP@TSSOP20(single ISP) [DX0001]
R5F211A4DSP@TSSOP20(single wire) [DX1000]
R5F211A4DSP@TSSOP20(UART ISP) [DX0001]
R5F211A4DSP@TSSOP20(UART mode) [DX1000]
R5F211A4NP@QFN28 [DX4013]
R5F211A4NP@QFN28(single ISP) [DX0001]
R5F211A4NP@QFN28(single wire) [DX4013]
R5F211A4NP@QFN28(UART ISP) [DX0001]
R5F211A4NP@QFN28(UART mode) [DX4013]
R5F211A4SP@TSSOP20 [DX1000]
R5F211A4SP@TSSOP20(single ISP) [DX0001]
R5F211A4SP@TSSOP20(single wire) [DX1000]
R5F211A4SP@TSSOP20(UART ISP) [DX0001]
R5F211A4SP@TSSOP20(UART mode) [DX1000]
R5F211B1DD@SDIP20 [DX0032]
R5F211B1DD@SDIP20(single ISP) [DX0001]
R5F211B1DD@SDIP20(single wire) [DX0032]
R5F211B1DD@SDIP20(UART ISP) [DX0001]
R5F211B1DD@SDIP20(UART mode) [DX0032]
R5F211B1DSP@TSSOP20 [DX1000]
R5F211B1DSP@TSSOP20(single ISP) [DX0001]
R5F211B1DSP@TSSOP20(single wire) [DX1000]
R5F211B1DSP@TSSOP20(UART ISP) [DX0001]
R5F211B1DSP@TSSOP20(UART mode) [DX1000]
R5F211B1SP@TSSOP20 [DX1000]
R5F211B1SP@TSSOP20(single ISP) [DX0001]
R5F211B1SP@TSSOP20(single wire) [DX1000]
R5F211B1SP@TSSOP20(UART ISP) [DX0001]
R5F211B1SP@TSSOP20(UART mode) [DX1000]
R5F211B2DD@SDIP20 [DX0032]
R5F211B2DD@SDIP20(single ISP) [DX0001]
R5F211B2DD@SDIP20(single wire) [DX0032]
R5F211B2DD@SDIP20(UART ISP) [DX0001]
R5F211B2DD@SDIP20(UART mode) [DX0032]
R5F211B2DSP@TSSOP20 [DX1000]
R5F211B2DSP@TSSOP20(single ISP) [DX0001]
R5F211B2DSP@TSSOP20(single wire) [DX1000]
R5F211B2DSP@TSSOP20(UART ISP) [DX0001]
R5F211B2DSP@TSSOP20(UART mode) [DX1000]
R5F211B2NP@QFN28 [DX4013]

R5F211B2NP@QFN28(single ISP) [DX0001]
R5F211B2NP@QFN28(single wire) [DX4013]
R5F211B2NP@QFN28(UART ISP) [DX0001]
R5F211B2NP@QFN28(UART mode) [DX4013]
R5F211B2SP@TSSOP20 [DX1000]
R5F211B2SP@TSSOP20(single ISP) [DX0001]
R5F211B2SP@TSSOP20(single wire) [DX1000]
R5F211B2SP@TSSOP20(UART ISP) [DX0001]
R5F211B2SP@TSSOP20(UART mode) [DX1000]
R5F211B3DD@SDIP20 [DX0032]
R5F211B3DD@SDIP20(single ISP) [DX0001]
R5F211B3DD@SDIP20(single wire) [DX0032]
R5F211B3DD@SDIP20(UART ISP) [DX0001]
R5F211B3DD@SDIP20(UART mode) [DX0032]
R5F211B3DSP@TSSOP20 [DX1000]
R5F211B3DSP@TSSOP20(single ISP) [DX0001]
R5F211B3DSP@TSSOP20(single wire) [DX1000]
R5F211B3DSP@TSSOP20(UART ISP) [DX0001]
R5F211B3DSP@TSSOP20(UART mode) [DX1000]
R5F211B3NP@QFN28 [DX4013]
R5F211B3NP@QFN28(single ISP) [DX0001]
R5F211B3NP@QFN28(single wire) [DX4013]
R5F211B3NP@QFN28(UART ISP) [DX0001]
R5F211B3NP@QFN28(UART mode) [DX4013]
R5F211B3SP@TSSOP20 [DX1000]
R5F211B3SP@TSSOP20(single ISP) [DX0001]
R5F211B3SP@TSSOP20(single wire) [DX1000]
R5F211B3SP@TSSOP20(UART ISP) [DX0001]
R5F211B3SP@TSSOP20(UART mode) [DX1000]
R5F211B4DD@SDIP20 [DX0032]
R5F211B4DD@SDIP20(single ISP) [DX0001]
R5F211B4DD@SDIP20(single wire) [DX0032]
R5F211B4DD@SDIP20(UART ISP) [DX0001]
R5F211B4DD@SDIP20(UART mode) [DX0032]
R5F211B4DSP@TSSOP20 [DX1000]
R5F211B4DSP@TSSOP20(single ISP) [DX0001]
R5F211B4DSP@TSSOP20(single wire) [DX1000]
R5F211B4DSP@TSSOP20(UART ISP) [DX0001]
R5F211B4DSP@TSSOP20(UART mode) [DX1000]
R5F211B4NP@QFN28 [DX4013]
R5F211B4NP@QFN28(single ISP) [DX0001]
R5F211B4NP@QFN28(single wire) [DX4013]
R5F211B4NP@QFN28(UART ISP) [DX0001]
R5F211B4NP@QFN28(UART mode) [DX4013]
R5F211B4SP@TSSOP20 [DX1000]
R5F211B4SP@TSSOP20(single ISP) [DX0001]
R5F211B4SP@TSSOP20(single wire) [DX1000]
R5F211B4SP@TSSOP20(UART ISP) [DX0001]

R5F211B4SP@TSSOP20(UART mode) [DX1000]
R5F21206JFP@TQFP48 [DX3007]
R5F21206JFP@TQFP48(single ISP) [DX0001]
R5F21206JFP@TQFP48(single wire) [DX3007]
R5F21206KFP@TQFP48 [DX3007]
R5F21206KFP@TQFP48(single ISP) [DX0001]
R5F21206KFP@TQFP48(single wire) [DX3007]
R5F21207JFP@TQFP48 [DX3007]
R5F21207JFP@TQFP48(single ISP) [DX0001]
R5F21207JFP@TQFP48(single wire) [DX3007]
R5F21207KFP@TQFP48 [DX3007]
R5F21207KFP@TQFP48(single ISP) [DX0001]
R5F21207KFP@TQFP48(single wire) [DX3007]
R5F21208JFP@TQFP48 [DX3007]
R5F21208JFP@TQFP48(single ISP) [DX0001]
R5F21208JFP@TQFP48(single wire) [DX3007]
R5F21208KFP@TQFP48 [DX3007]
R5F21208KFP@TQFP48(single ISP) [DX0001]
R5F21208KFP@TQFP48(single wire) [DX3007]
R5F2120AJFP@TQFP48 [DX3007]
R5F2120AJFP@TQFP48(single ISP) [DX0001]
R5F2120AJFP@TQFP48(single wire) [DX3007]
R5F2120AKFP@TQFP48 [DX3007]
R5F2120AKFP@TQFP48(single ISP) [DX0001]
R5F2120AKFP@TQFP48(single wire) [DX3007]
R5F2120CJFP@TQFP48 [DX3007]
R5F2120CJFP@TQFP48(single ISP) [DX0001]
R5F2120CJFP@TQFP48(single wire) [DX3007]
R5F2120CKFP@TQFP48 [DX3007]
R5F2120CKFP@TQFP48(single ISP) [DX0001]
R5F2120CKFP@TQFP48(single wire) [DX3007]
R5F21216JFP@TQFP48 [DX3007]
R5F21216JFP@TQFP48(single ISP) [DX0001]
R5F21216JFP@TQFP48(single wire) [DX3007]
R5F21216KFP@TQFP48 [DX3007]
R5F21216KFP@TQFP48(single ISP) [DX0001]
R5F21216KFP@TQFP48(single wire) [DX3007]
R5F21217JFP@TQFP48 [DX3007]
R5F21217JFP@TQFP48(single ISP) [DX0001]
R5F21217JFP@TQFP48(single wire) [DX3007]
R5F21217KFP@TQFP48 [DX3007]
R5F21217KFP@TQFP48(single ISP) [DX0001]
R5F21217KFP@TQFP48(single wire) [DX3007]
R5F21218JFP@TQFP48 [DX3007]
R5F21218JFP@TQFP48(single ISP) [DX0001]
R5F21218JFP@TQFP48(single wire) [DX3007]
R5F21218KFP@TQFP48 [DX3007]
R5F21218KFP@TQFP48(single ISP) [DX0001]

R5F21218KFP@TQFP48(single wire) [DX3007]
R5F2121AJFP@TQFP48 [DX3007]
R5F2121AJFP@TQFP48(single ISP) [DX0001]
R5F2121AJFP@TQFP48(single wire) [DX3007]
R5F2121AKFP@TQFP48 [DX3007]
R5F2121AKFP@TQFP48(single ISP) [DX0001]
R5F2121AKFP@TQFP48(single wire) [DX3007]
R5F2121CJFP@TQFP48 [DX3007]
R5F2121CJFP@TQFP48(single ISP) [DX0001]
R5F2121CJFP@TQFP48(single wire) [DX3007]
R5F2121CKFP@TQFP48 [DX3007]
R5F2121CKFP@TQFP48(single ISP) [DX0001]
R5F2121CKFP@TQFP48(single wire) [DX3007]
R5F21226JFP@TQFP48 [DX3007]
R5F21226JFP@TQFP48(single ISP) [DX0001]
R5F21226JFP@TQFP48(single wire) [DX3007]
R5F21226KFP@TQFP48 [DX3007]
R5F21226KFP@TQFP48(single ISP) [DX0001]
R5F21226KFP@TQFP48(single wire) [DX3007]
R5F21227JFP@TQFP48 [DX3007]
R5F21227JFP@TQFP48(single ISP) [DX0001]
R5F21227JFP@TQFP48(single wire) [DX3007]
R5F21227KFP@TQFP48 [DX3007]
R5F21227KFP@TQFP48(single ISP) [DX0001]
R5F21227KFP@TQFP48(single wire) [DX3007]
R5F21228JFP@TQFP48 [DX3007]
R5F21228JFP@TQFP48(single ISP) [DX0001]
R5F21228JFP@TQFP48(single wire) [DX3007]
R5F21228KFP@TQFP48 [DX3007]
R5F21228KFP@TQFP48(single ISP) [DX0001]
R5F21228KFP@TQFP48(single wire) [DX3007]
R5F2122AJFP@TQFP48 [DX3007]
R5F2122AJFP@TQFP48(single ISP) [DX0001]
R5F2122AJFP@TQFP48(single wire) [DX3007]
R5F2122AKFP@TQFP48 [DX3007]
R5F2122AKFP@TQFP48(single ISP) [DX0001]
R5F2122AKFP@TQFP48(single wire) [DX3007]
R5F2122CJFP@TQFP48 [DX3007]
R5F2122CJFP@TQFP48(single ISP) [DX0001]
R5F2122CJFP@TQFP48(single wire) [DX3007]
R5F2122CKFP@TQFP48 [DX3007]
R5F2122CKFP@TQFP48(single ISP) [DX0001]
R5F2122CKFP@TQFP48(single wire) [DX3007]
R5F21236DFP@TQFP48 [DX3007]
R5F21236DFP@TQFP48(single wire) [DX3007]
R5F21236JFP@TQFP48 [DX3007]
R5F21236JFP@TQFP48(single ISP) [DX0001]
R5F21236JFP@TQFP48(single wire) [DX3007]

R5F21236KFP@TQFP48 [DX3007]
R5F21236KFP@TQFP48(single ISP) [DX0001]
R5F21236KFP@TQFP48(single wire) [DX3007]
R5F21237JFP@TQFP48 [DX3007]
R5F21237JFP@TQFP48(single ISP) [DX0001]
R5F21237JFP@TQFP48(single wire) [DX3007]
R5F21237KFP@TQFP48 [DX3007]
R5F21237KFP@TQFP48(single ISP) [DX0001]
R5F21237KFP@TQFP48(single wire) [DX3007]
R5F21238JFP@TQFP48 [DX3007]
R5F21238JFP@TQFP48(single ISP) [DX0001]
R5F21238JFP@TQFP48(single wire) [DX3007]
R5F21238KFP@TQFP48 [DX3007]
R5F21238KFP@TQFP48(single ISP) [DX0001]
R5F21238KFP@TQFP48(single wire) [DX3007]
R5F2123AJFP@TQFP48 [DX3007]
R5F2123AJFP@TQFP48(single ISP) [DX0001]
R5F2123AJFP@TQFP48(single wire) [DX3007]
R5F2123AKFP@TQFP48 [DX3007]
R5F2123AKFP@TQFP48(single ISP) [DX0001]
R5F2123AKFP@TQFP48(single wire) [DX3007]
R5F2123CJFP@TQFP48 [DX3007]
R5F2123CJFP@TQFP48(single ISP) [DX0001]
R5F2123CJFP@TQFP48(single wire) [DX3007]
R5F2123CKFP@TQFP48 [DX3007]
R5F2123CKFP@TQFP48(single ISP) [DX0001]
R5F2123CKFP@TQFP48(single wire) [DX3007]
R5F21244SDFP@TQFP52 [DX3010]
R5F21244SDFP@TQFP52(single ISP) [DX0001]
R5F21244SDFP@TQFP52(single wire) [DX3010]
R5F21244SDFP@TQFP52(UART ISP) [DX0001]
R5F21244SDFP@TQFP52(UART mode) [DX3010]
R5F21244SNFP@TQFP52 [DX3010]
R5F21244SNFP@TQFP52(single ISP) [DX0001]
R5F21244SNFP@TQFP52(single wire) [DX3010]
R5F21244SNFP@TQFP52(UART ISP) [DX0001]
R5F21244SNFP@TQFP52(UART mode) [DX3010]
R5F21245SDFP@TQFP52 [DX3010]
R5F21245SDFP@TQFP52(single wire) [DX3010]
R5F21245SDFP@TQFP52(UART ISP) [DX0001]
R5F21245SDFP@TQFP52(UART mode) [DX3010]
R5F21245SNFP@TQFP52 [DX3010]
R5F21245SNFP@TQFP52(single wire) [DX3010]
R5F21245SNFP@TQFP52(UART ISP) [DX0001]
R5F21245SNFP@TQFP52(UART mode) [DX3010]
R5F21246SDFP@TQFP52 [DX3010]
R5F21246SDFP@TQFP52(single ISP) [DX0001]
R5F21246SDFP@TQFP52(single wire) [DX3010]

R5F21246SDFP@TQFP52(UART ISP) [DX0001]
R5F21246SDFP@TQFP52(UART mode) [DX3010]
R5F21246SNFP@TQFP52 [DX3010]
R5F21246SNFP@TQFP52(single ISP) [DX0001]
R5F21246SNFP@TQFP52(single wire) [DX3010]
R5F21246SNFP@TQFP52(UART ISP) [DX0001]
R5F21246SNFP@TQFP52(UART mode) [DX3010]
R5F21247SDFP@TQFP52 [DX3010]
R5F21247SDFP@TQFP52(single ISP) [DX0001]
R5F21247SDFP@TQFP52(single wire) [DX3010]
R5F21247SDFP@TQFP52(UART ISP) [DX0001]
R5F21247SDFP@TQFP52(UART mode) [DX3010]
R5F21247SNFP@TQFP52 [DX3010]
R5F21247SNFP@TQFP52(single ISP) [DX0001]
R5F21247SNFP@TQFP52(single wire) [DX3010]
R5F21247SNFP@TQFP52(UART ISP) [DX0001]
R5F21247SNFP@TQFP52(UART mode) [DX3010]
R5F21248SDFP@TQFP52 [DX3010]
R5F21248SDFP@TQFP52(single ISP) [DX0001]
R5F21248SDFP@TQFP52(single wire) [DX3010]
R5F21248SDFP@TQFP52(UART ISP) [DX0001]
R5F21248SDFP@TQFP52(UART mode) [DX3010]
R5F21248SNFP@TQFP52 [DX3010]
R5F21248SNFP@TQFP52(single ISP) [DX0001]
R5F21248SNFP@TQFP52(single wire) [DX3010]
R5F21248SNFP@TQFP52(UART ISP) [DX0001]
R5F21248SNFP@TQFP52(UART mode) [DX3010]
R5F21254SDFP@TQFP52 [DX3010]
R5F21254SDFP@TQFP52(single ISP) [DX0001]
R5F21254SDFP@TQFP52(single wire) [DX3010]
R5F21254SDFP@TQFP52(UART ISP) [DX0001]
R5F21254SDFP@TQFP52(UART mode) [DX3010]
R5F21254SNFP@TQFP52 [DX3010]
R5F21254SNFP@TQFP52(single ISP) [DX0001]
R5F21254SNFP@TQFP52(single wire) [DX3010]
R5F21254SNFP@TQFP52(UART ISP) [DX0001]
R5F21254SNFP@TQFP52(UART mode) [DX3010]
R5F21254SYFP@TQFP52 [DX3010]　　R5F21255SDFP@TQFP52 [DX3010]
R5F21255SDFP@TQFP52(single wire) [DX3010]
R5F21255SDFP@TQFP52(UART mode) [DX3010]
R5F21255SNFP@TQFP52 [DX3010]
R5F21255SNFP@TQFP52(single wire) [DX3010]
R5F21255SNFP@TQFP52(UART mode) [DX3010]
R5F21255SYFP@TQFP52 [DX3010]　　R5F21256SDFP@TQFP52 [DX3010]
R5F21256SDFP@TQFP52(single ISP) [DX0001]
R5F21256SDFP@TQFP52(single wire) [DX3010]
R5F21256SDFP@TQFP52(UART ISP) [DX0001]
R5F21256SDFP@TQFP52(UART mode) [DX3010]

R5F21256SNFP@TQFP52 [DX3010]
R5F21256SNFP@TQFP52(single ISP) [DX0001]
R5F21256SNFP@TQFP52(single wire) [DX3010]
R5F21256SNFP@TQFP52(UART ISP) [DX0001]
R5F21256SNFP@TQFP52(UART mode) [DX3010]
R5F21256SYFP@TQFP52 [DX3010]　　R5F21257SDFP@TQFP52 [DX3010]
R5F21257SDFP@TQFP52(single ISP) [DX0001]
R5F21257SDFP@TQFP52(single wire) [DX3010]
R5F21257SDFP@TQFP52(UART ISP) [DX0001]
R5F21257SDFP@TQFP52(UART mode) [DX3010]
R5F21257SNFP@TQFP52 [DX3010]
R5F21257SNFP@TQFP52(single ISP) [DX0001]
R5F21257SNFP@TQFP52(single wire) [DX3010]
R5F21257SNFP@TQFP52(UART ISP) [DX0001]
R5F21257SNFP@TQFP52(UART mode) [DX3010]
R5F21257SYFP@TQFP52 [DX3010]　　R5F21258SDFP@TQFP52 [DX3010]
R5F21258SDFP@TQFP52(single ISP) [DX0001]
R5F21258SDFP@TQFP52(single wire) [DX3010]
R5F21258SDFP@TQFP52(UART ISP) [DX0001]
R5F21258SDFP@TQFP52(UART mode) [DX3010]
R5F21258SNFP@TQFP52 [DX3010]
R5F21258SNFP@TQFP52(single ISP) [DX0001]
R5F21258SNFP@TQFP52(single wire) [DX3010]
R5F21258SNFP@TQFP52(UART ISP) [DX0001]
R5F21258SNFP@TQFP52(UART mode) [DX3010]
R5F21258SYFP@TQFP52 [DX3010]　　R5F21262DFP@QFP32 [DX3061]
R5F21262DFP@QFP32(single ISP) [DX0001]
R5F21262DFP@QFP32(single wire) [DX3061]
R5F21262DFP@QFP32(UART ISP) [DX0001]
R5F21262DFP@QFP32(UART mode) [DX3061]
R5F21262JFP@QFP32 [DX3061]
R5F21262JFP@QFP32(single ISP) [DX0001]
R5F21262JFP@QFP32(single wire) [DX3061]
R5F21262JFP@QFP32(UART ISP) [DX0001]
R5F21262JFP@QFP32(UART mode) [DX3061]
R5F21262KFP@QFP32 [DX3061]
R5F21262KFP@QFP32(single ISP) [DX0001]
R5F21262KFP@QFP32(single wire) [DX3061]
R5F21262KFP@QFP32(UART ISP) [DX0001]
R5F21262KFP@QFP32(UART mode) [DX3061]
R5F21262NFP@QFP32 [DX3061]
R5F21262NFP@QFP32(single ISP) [DX0001]
R5F21262NFP@QFP32(single wire) [DX3061]
R5F21262NFP@QFP32(UART ISP) [DX0001]
R5F21262NFP@QFP32(UART mode) [DX3061]
R5F21262SDFP@QFP32 [DX3061]
R5F21262SDFP@QFP32(single ISP) [DX0001]
R5F21262SDFP@QFP32(single wire) [DX3061]

R5F21262SDFP@QFP32(UART ISP) [DX0001]
R5F21262SDFP@QFP32(UART mode) [DX3061]
R5F21262SJFP@QFP32 [DX3061]
R5F21262SJFP@QFP32(single ISP) [DX0001]
R5F21262SJFP@QFP32(single wire) [DX3061]
R5F21262SJFP@QFP32(UART ISP) [DX0001]
R5F21262SJFP@QFP32(UART mode) [DX3061]
R5F21262SKFP@QFP32 [DX3061]
R5F21262SKFP@QFP32(single ISP) [DX0001]
R5F21262SKFP@QFP32(single wire) [DX3061]
R5F21262SKFP@QFP32(UART ISP) [DX0001]
R5F21262SKFP@QFP32(UART mode) [DX3061]
R5F21262SNFP@QFP32 [DX3061]
R5F21262SNFP@QFP32(single ISP) [DX0001]
R5F21262SNFP@QFP32(single wire) [DX3061]
R5F21262SNFP@QFP32(UART ISP) [DX0001]
R5F21262SNFP@QFP32(UART mode) [DX3061]
R5F21264DFP@QFP32 [DX3061]
R5F21264DFP@QFP32(single ISP) [DX0001]
R5F21264DFP@QFP32(single wire) [DX3061]
R5F21264DFP@QFP32(UART ISP) [DX0001]
R5F21264DFP@QFP32(UART mode) [DX3061]
R5F21264JFP@QFP32 [DX3061]
R5F21264JFP@QFP32(single ISP) [DX0001]
R5F21264JFP@QFP32(single wire) [DX3061]
R5F21264JFP@QFP32(UART ISP) [DX0001]
R5F21264JFP@QFP32(UART mode) [DX3061]
R5F21264KFP@QFP32 [DX3061]
R5F21264KFP@QFP32(single ISP) [DX0001]
R5F21264KFP@QFP32(single wire) [DX3061]
R5F21264KFP@QFP32(UART ISP) [DX0001]
R5F21264KFP@QFP32(UART mode) [DX3061]
R5F21264NFP@QFP32 [DX3061]
R5F21264NFP@QFP32(single ISP) [DX0001]
R5F21264NFP@QFP32(single wire) [DX3061]
R5F21264NFP@QFP32(UART ISP) [DX0001]
R5F21264NFP@QFP32(UART mode) [DX3061]
R5F21264SDFP@QFP32 [DX3061]
R5F21264SDFP@QFP32(single ISP) [DX0001]
R5F21264SDFP@QFP32(single wire) [DX3061]
R5F21264SDFP@QFP32(UART ISP) [DX0001]
R5F21264SDFP@QFP32(UART mode) [DX3061]
R5F21264SJFP@QFP32 [DX3061]
R5F21264SJFP@QFP32(single ISP) [DX0001]
R5F21264SJFP@QFP32(single wire) [DX3061]
R5F21264SJFP@QFP32(UART ISP) [DX0001]
R5F21264SJFP@QFP32(UART mode) [DX3061]
R5F21264SKFP@QFP32 [DX3061]

R5F21264SKFP@QFP32(single ISP) [DX0001]
R5F21264SKFP@QFP32(single wire) [DX3061]
R5F21264SKFP@QFP32(UART ISP) [DX0001]
R5F21264SKFP@QFP32(UART mode) [DX3061]
R5F21264SNFP@QFP32 [DX3061]
R5F21264SNFP@QFP32(single ISP) [DX0001]
R5F21264SNFP@QFP32(single wire) [DX3061]
R5F21264SNFP@QFP32(UART ISP) [DX0001]
R5F21264SNFP@QFP32(UART mode) [DX3061]
R5F21265DFP@QFP32 [DX3061]
R5F21265DFP@QFP32(single ISP) [DX0001]
R5F21265DFP@QFP32(single wire) [DX3061]
R5F21265DFP@QFP32(UART ISP) [DX0001]
R5F21265DFP@QFP32(UART mode) [DX3061]
R5F21265JFP@QFP32 [DX3061]
R5F21265JFP@QFP32(single ISP) [DX0001]
R5F21265JFP@QFP32(single wire) [DX3061]
R5F21265JFP@QFP32(UART ISP) [DX0001]
R5F21265JFP@QFP32(UART mode) [DX3061]
R5F21265KFP@QFP32 [DX3061]
R5F21265KFP@QFP32(single ISP) [DX0001]
R5F21265KFP@QFP32(single wire) [DX3061]
R5F21265KFP@QFP32(UART ISP) [DX0001]
R5F21265KFP@QFP32(UART mode) [DX3061]
R5F21265NFP@QFP32 [DX3061]
R5F21265NFP@QFP32(single ISP) [DX0001]
R5F21265NFP@QFP32(single wire) [DX3061]
R5F21265NFP@QFP32(UART ISP) [DX0001]
R5F21265NFP@QFP32(UART mode) [DX3061]
R5F21265SDFP@QFP32 [DX3061]
R5F21265SDFP@QFP32(single ISP) [DX0001]
R5F21265SDFP@QFP32(single wire) [DX3061]
R5F21265SDFP@QFP32(UART ISP) [DX0001]
R5F21265SDFP@QFP32(UART mode) [DX3061]
R5F21265SJFP@QFP32 [DX3061]
R5F21265SJFP@QFP32(single ISP) [DX0001]
R5F21265SJFP@QFP32(single wire) [DX3061]
R5F21265SJFP@QFP32(UART ISP) [DX0001]
R5F21265SJFP@QFP32(UART mode) [DX3061]
R5F21265SKFP@QFP32 [DX3061]
R5F21265SKFP@QFP32(single ISP) [DX0001]
R5F21265SKFP@QFP32(single wire) [DX3061]
R5F21265SKFP@QFP32(UART ISP) [DX0001]
R5F21265SKFP@QFP32(UART mode) [DX3061]
R5F21265SNFP@QFP32 [DX3061]
R5F21265SNFP@QFP32(single ISP) [DX0001]
R5F21265SNFP@QFP32(single wire) [DX3061]
R5F21265SNFP@QFP32(UART ISP) [DX0001]

R5F21265SNFP@QFP32(UART mode) [DX3061]
R5F21266DFP@QFP32 [DX3061]
R5F21266DFP@QFP32(single ISP) [DX0001]
R5F21266DFP@QFP32(single wire) [DX3061]
R5F21266DFP@QFP32(UART ISP) [DX0001]
R5F21266DFP@QFP32(UART mode) [DX3061]
R5F21266JFP@QFP32 [DX3061]
R5F21266JFP@QFP32(single ISP) [DX0001]
R5F21266JFP@QFP32(single wire) [DX3061]
R5F21266JFP@QFP32(UART ISP) [DX0001]
R5F21266JFP@QFP32(UART mode) [DX3061]
R5F21266KFP@QFP32 [DX3061]
R5F21266KFP@QFP32(single ISP) [DX0001]
R5F21266KFP@QFP32(single wire) [DX3061]
R5F21266KFP@QFP32(UART ISP) [DX0001]
R5F21266KFP@QFP32(UART mode) [DX3061]
R5F21266NFP@QFP32 [DX3061]
R5F21266NFP@QFP32(single ISP) [DX0001]
R5F21266NFP@QFP32(single wire) [DX3061]
R5F21266NFP@QFP32(UART ISP) [DX0001]
R5F21266NFP@QFP32(UART mode) [DX3061]
R5F21266SDFP@QFP32 [DX3061]
R5F21266SDFP@QFP32(single ISP) [DX0001]
R5F21266SDFP@QFP32(single wire) [DX3061]
R5F21266SDFP@QFP32(UART ISP) [DX0001]
R5F21266SDFP@QFP32(UART mode) [DX3061]
R5F21266SJFP@QFP32 [DX3061]
R5F21266SJFP@QFP32(single ISP) [DX0001]
R5F21266SJFP@QFP32(single wire) [DX3061]
R5F21266SJFP@QFP32(UART ISP) [DX0001]
R5F21266SJFP@QFP32(UART mode) [DX3061]
R5F21266SKFP@QFP32 [DX3061]
R5F21266SKFP@QFP32(single ISP) [DX0001]
R5F21266SKFP@QFP32(single wire) [DX3061]
R5F21266SKFP@QFP32(UART ISP) [DX0001]
R5F21266SKFP@QFP32(UART mode) [DX3061]
R5F21266SNFP@QFP32 [DX3061]
R5F21266SNFP@QFP32(single ISP) [DX0001]
R5F21266SNFP@QFP32(single wire) [DX3061]
R5F21266SNFP@QFP32(UART ISP) [DX0001]
R5F21266SNFP@QFP32(UART mode) [DX3061]
R5F21272DFP@QFP32 [DX3061]
R5F21272DFP@QFP32(single ISP) [DX0001]
R5F21272DFP@QFP32(single wire) [DX3061]
R5F21272DFP@QFP32(UART ISP) [DX0001]
R5F21272DFP@QFP32(UART mode) [DX3061]
R5F21272JFP@QFP32 [DX3061]
R5F21272JFP@QFP32(single ISP) [DX0001]

R5F21272JFP@QFP32(single wire) [DX3061]
R5F21272JFP@QFP32(UART ISP) [DX0001]
R5F21272JFP@QFP32(UART mode) [DX3061]
R5F21272KFP@QFP32 [DX3061]
R5F21272KFP@QFP32(single ISP) [DX0001]
R5F21272KFP@QFP32(single wire) [DX3061]
R5F21272KFP@QFP32(UART ISP) [DX0001]
R5F21272KFP@QFP32(UART mode) [DX3061]
R5F21272NFP@QFP32 [DX3061]
R5F21272NFP@QFP32(single ISP) [DX0001]
R5F21272NFP@QFP32(single wire) [DX3061]
R5F21272NFP@QFP32(UART ISP) [DX0001]
R5F21272NFP@QFP32(UART mode) [DX3061]
R5F21272SDFP@QFP32 [DX3061]
R5F21272SDFP@QFP32(single ISP) [DX0001]
R5F21272SDFP@QFP32(single wire) [DX3061]
R5F21272SDFP@QFP32(UART ISP) [DX0001]
R5F21272SDFP@QFP32(UART mode) [DX3061]
R5F21272SJFP@QFP32 [DX3061]
R5F21272SJFP@QFP32(single ISP) [DX0001]
R5F21272SJFP@QFP32(single wire) [DX3061]
R5F21272SJFP@QFP32(UART ISP) [DX0001]
R5F21272SJFP@QFP32(UART mode) [DX3061]
R5F21272SKFP@QFP32 [DX3061]
R5F21272SKFP@QFP32(single ISP) [DX0001]
R5F21272SKFP@QFP32(single wire) [DX3061]
R5F21272SKFP@QFP32(UART ISP) [DX0001]
R5F21272SKFP@QFP32(UART mode) [DX3061]
R5F21272SNFP@QFP32 [DX3061]
R5F21272SNFP@QFP32(single ISP) [DX0001]
R5F21272SNFP@QFP32(single wire) [DX3061]
R5F21272SNFP@QFP32(UART ISP) [DX0001]
R5F21272SNFP@QFP32(UART mode) [DX3061]
R5F21274DFP@QFP32 [DX3061]
R5F21274DFP@QFP32(single ISP) [DX0001]
R5F21274DFP@QFP32(single wire) [DX3061]
R5F21274DFP@QFP32(UART ISP) [DX0001]
R5F21274DFP@QFP32(UART mode) [DX3061]
R5F21274JFP@QFP32 [DX3061]
R5F21274JFP@QFP32(single ISP) [DX0001]
R5F21274JFP@QFP32(single wire) [DX3061]
R5F21274JFP@QFP32(UART ISP) [DX0001]
R5F21274JFP@QFP32(UART mode) [DX3061]
R5F21274KFP@QFP32 [DX3061]
R5F21274KFP@QFP32(single ISP) [DX0001]
R5F21274KFP@QFP32(single wire) [DX3061]
R5F21274KFP@QFP32(UART ISP) [DX0001]
R5F21274KFP@QFP32(UART mode) [DX3061]

R5F21274NFP@QFP32 [DX3061]
R5F21274NFP@QFP32(single ISP) [DX0001]
R5F21274NFP@QFP32(single wire) [DX3061]
R5F21274NFP@QFP32(UART ISP) [DX0001]
R5F21274NFP@QFP32(UART mode) [DX3061]
R5F21274SDFP@QFP32 [DX3061]
R5F21274SDFP@QFP32(single ISP) [DX0001]
R5F21274SDFP@QFP32(single wire) [DX3061]
R5F21274SDFP@QFP32(UART ISP) [DX0001]
R5F21274SDFP@QFP32(UART mode) [DX3061]
R5F21274SJFP@QFP32 [DX3061]
R5F21274SJFP@QFP32(single ISP) [DX0001]
R5F21274SJFP@QFP32(single wire) [DX3061]
R5F21274SJFP@QFP32(UART ISP) [DX0001]
R5F21274SJFP@QFP32(UART mode) [DX3061]
R5F21274SKFP@QFP32 [DX3061]
R5F21274SKFP@QFP32(single ISP) [DX0001]
R5F21274SKFP@QFP32(single wire) [DX3061]
R5F21274SKFP@QFP32(UART ISP) [DX0001]
R5F21274SKFP@QFP32(UART mode) [DX3061]
R5F21274SNFP@QFP32 [DX3061]
R5F21274SNFP@QFP32(single ISP) [DX0001]
R5F21274SNFP@QFP32(single wire) [DX3061]
R5F21274SNFP@QFP32(UART ISP) [DX0001]
R5F21274SNFP@QFP32(UART mode) [DX3061]
R5F21275DFP@QFP32 [DX3061]
R5F21275DFP@QFP32(single ISP) [DX0001]
R5F21275DFP@QFP32(single wire) [DX3061]
R5F21275DFP@QFP32(UART ISP) [DX0001]
R5F21275DFP@QFP32(UART mode) [DX3061]
R5F21275JFP@QFP32 [DX3061]
R5F21275JFP@QFP32(single ISP) [DX0001]
R5F21275JFP@QFP32(single wire) [DX3061]
R5F21275JFP@QFP32(UART ISP) [DX0001]
R5F21275JFP@QFP32(UART mode) [DX3061]
R5F21275KFP@QFP32 [DX3061]
R5F21275KFP@QFP32(single ISP) [DX0001]
R5F21275KFP@QFP32(single wire) [DX3061]
R5F21275KFP@QFP32(UART ISP) [DX0001]
R5F21275KFP@QFP32(UART mode) [DX3061]
R5F21275NFP@QFP32 [DX3061]
R5F21275NFP@QFP32(single ISP) [DX0001]
R5F21275NFP@QFP32(single wire) [DX3061]
R5F21275NFP@QFP32(UART ISP) [DX0001]
R5F21275NFP@QFP32(UART mode) [DX3061]
R5F21275SDFP@QFP32 [DX3061]
R5F21275SDFP@QFP32(single ISP) [DX0001]
R5F21275SDFP@QFP32(single wire) [DX3061]

R5F21275SDFP@QFP32(UART ISP) [DX0001]
R5F21275SDFP@QFP32(UART mode) [DX3061]
R5F21275SJFP@QFP32 [DX3061]
R5F21275SJFP@QFP32(single ISP) [DX0001]
R5F21275SJFP@QFP32(single wire) [DX3061]
R5F21275SJFP@QFP32(UART ISP) [DX0001]
R5F21275SJFP@QFP32(UART mode) [DX3061]
R5F21275SKFP@QFP32 [DX3061]
R5F21275SKFP@QFP32(single ISP) [DX0001]
R5F21275SKFP@QFP32(single wire) [DX3061]
R5F21275SKFP@QFP32(UART ISP) [DX0001]
R5F21275SKFP@QFP32(UART mode) [DX3061]
R5F21275SNFP@QFP32 [DX3061]
R5F21275SNFP@QFP32(single ISP) [DX0001]
R5F21275SNFP@QFP32(single wire) [DX3061]
R5F21275SNFP@QFP32(UART ISP) [DX0001]
R5F21275SNFP@QFP32(UART mode) [DX3061]
R5F21276DFP@QFP32 [DX3061]
R5F21276DFP@QFP32(single ISP) [DX0001]
R5F21276DFP@QFP32(single wire) [DX3061]
R5F21276DFP@QFP32(UART ISP) [DX0001]
R5F21276DFP@QFP32(UART mode) [DX3061]
R5F21276JFP@QFP32 [DX3061]
R5F21276JFP@QFP32(single ISP) [DX0001]
R5F21276JFP@QFP32(single wire) [DX3061]
R5F21276JFP@QFP32(UART ISP) [DX0001]
R5F21276JFP@QFP32(UART mode) [DX3061]
R5F21276KFP@QFP32 [DX3061]
R5F21276KFP@QFP32(single ISP) [DX0001]
R5F21276KFP@QFP32(single wire) [DX3061]
R5F21276KFP@QFP32(UART ISP) [DX0001]
R5F21276KFP@QFP32(UART mode) [DX3061]
R5F21276NFP@QFP32 [DX3061]
R5F21276NFP@QFP32(single ISP) [DX0001]
R5F21276NFP@QFP32(single wire) [DX3061]
R5F21276NFP@QFP32(UART ISP) [DX0001]
R5F21276NFP@QFP32(UART mode) [DX3061]
R5F21276SDFP@QFP32 [DX3061]
R5F21276SDFP@QFP32(single ISP) [DX0001]
R5F21276SDFP@QFP32(single wire) [DX3061]
R5F21276SDFP@QFP32(UART ISP) [DX0001]
R5F21276SDFP@QFP32(UART mode) [DX3061]
R5F21276SJFP@QFP32 [DX3061]
R5F21276SJFP@QFP32(single ISP) [DX0001]
R5F21276SJFP@QFP32(single wire) [DX3061]
R5F21276SJFP@QFP32(UART ISP) [DX0001]
R5F21276SJFP@QFP32(UART mode) [DX3061]
R5F21276SKFP@QFP32 [DX3061]

R5F21276SKFP@QFP32(single ISP) [DX0001]
R5F21276SKFP@QFP32(single wire) [DX3061]
R5F21276SKFP@QFP32(UART ISP) [DX0001]
R5F21276SKFP@QFP32(UART mode) [DX3061]
R5F21276SNFP@QFP32 [DX3061]
R5F21276SNFP@QFP32(single ISP) [DX0001]
R5F21276SNFP@QFP32(single wire) [DX3061]
R5F21276SNFP@QFP32(UART ISP) [DX0001]
R5F21276SNFP@QFP32(UART mode) [DX3061]
R5F21282DSP@SOIC20 [DX1000]
R5F21282DSP@SOIC20(single ISP) [DX0001]
R5F21282DSP@SOIC20(single wire) [DX1000]
R5F21282DSP@SOIC20(UART ISP) [DX0001]
R5F21282DSP@SOIC20(UART mode) [DX1000]
R5F21282JSP@SOIC20 [DX1000]
R5F21282JSP@SOIC20(single ISP) [DX0001]
R5F21282JSP@SOIC20(single wire) [DX1000]
R5F21282JSP@SOIC20(UART ISP) [DX0001]
R5F21282JSP@SOIC20(UART mode) [DX1000]
R5F21282KSP@SOIC20 [DX1000]
R5F21282KSP@SOIC20(single ISP) [DX0001]
R5F21282KSP@SOIC20(single wire) [DX1000]
R5F21282KSP@SOIC20(UART ISP) [DX0001]
R5F21282KSP@SOIC20(UART mode) [DX1000]
R5F21282NSP@SOIC20 [DX1000]
R5F21282NSP@SOIC20(single ISP) [DX0001]
R5F21282NSP@SOIC20(single wire) [DX1000]
R5F21282NSP@SOIC20(UART ISP) [DX0001]
R5F21282NSP@SOIC20(UART mode) [DX1000]
R5F21282SDSP@SOIC20 [DX1000]
R5F21282SDSP@SOIC20(single ISP) [DX0001]
R5F21282SDSP@SOIC20(single wire) [DX1000]
R5F21282SDSP@SOIC20(UART ISP) [DX0001]
R5F21282SDSP@SOIC20(UART mode) [DX1000]
R5F21282SJSP@SOIC20 [DX1000]
R5F21282SJSP@SOIC20(single ISP) [DX0001]
R5F21282SJSP@SOIC20(single wire) [DX1000]
R5F21282SJSP@SOIC20(UART ISP) [DX0001]
R5F21282SJSP@SOIC20(UART mode) [DX1000]
R5F21282SKSP@SOIC20 [DX1000]
R5F21282SKSP@SOIC20(single ISP) [DX0001]
R5F21282SKSP@SOIC20(single wire) [DX1000]
R5F21282SKSP@SOIC20(UART ISP) [DX0001]
R5F21282SKSP@SOIC20(UART mode) [DX1000]
R5F21282SNSP@SOIC20 [DX1000]
R5F21282SNSP@SOIC20(single ISP) [DX0001]
R5F21282SNSP@SOIC20(single wire) [DX1000]
R5F21282SNSP@SOIC20(UART ISP) [DX0001]

R5F21282SNSP@SOIC20(UART mode) [DX1000]
R5F21284DSP@SOIC20 [DX1000]
R5F21284DSP@SOIC20(single ISP) [DX0001]
R5F21284DSP@SOIC20(single wire) [DX1000]
R5F21284DSP@SOIC20(UART ISP) [DX0001]
R5F21284DSP@SOIC20(UART mode) [DX1000]
R5F21284JSP@SOIC20 [DX1000]
R5F21284JSP@SOIC20(single ISP) [DX0001]
R5F21284JSP@SOIC20(single wire) [DX1000]
R5F21284JSP@SOIC20(UART ISP) [DX0001]
R5F21284JSP@SOIC20(UART mode) [DX1000]
R5F21284KSP@SOIC20 [DX1000]
R5F21284KSP@SOIC20(single ISP) [DX0001]
R5F21284KSP@SOIC20(single wire) [DX1000]
R5F21284KSP@SOIC20(UART ISP) [DX0001]
R5F21284KSP@SOIC20(UART mode) [DX1000]
R5F21284NSP@SOIC20 [DX1000]
R5F21284NSP@SOIC20(single ISP) [DX0001]
R5F21284NSP@SOIC20(single wire) [DX1000]
R5F21284NSP@SOIC20(UART ISP) [DX0001]
R5F21284NSP@SOIC20(UART mode) [DX1000]
R5F21284SDSP@SOIC20 [DX1000]
R5F21284SDSP@SOIC20(single ISP) [DX0001]
R5F21284SDSP@SOIC20(single wire) [DX1000]
R5F21284SDSP@SOIC20(UART ISP) [DX0001]
R5F21284SDSP@SOIC20(UART mode) [DX1000]
R5F21284SJSP@SOIC20 [DX1000]
R5F21284SJSP@SOIC20(single ISP) [DX0001]
R5F21284SJSP@SOIC20(single wire) [DX1000]
R5F21284SJSP@SOIC20(UART ISP) [DX0001]
R5F21284SJSP@SOIC20(UART mode) [DX1000]
R5F21284SKSP@SOIC20 [DX1000]
R5F21284SKSP@SOIC20(single ISP) [DX0001]
R5F21284SKSP@SOIC20(single wire) [DX1000]
R5F21284SKSP@SOIC20(UART ISP) [DX0001]
R5F21284SKSP@SOIC20(UART mode) [DX1000]
R5F21284SNSP@SOIC20 [DX1000]
R5F21284SNSP@SOIC20(single ISP) [DX0001]
R5F21284SNSP@SOIC20(single wire) [DX1000]
R5F21284SNSP@SOIC20(UART ISP) [DX0001]
R5F21284SNSP@SOIC20(UART mode) [DX1000]
R5F21292DSP@SOIC20 [DX1000]
R5F21292DSP@SOIC20(single ISP) [DX0001]
R5F21292DSP@SOIC20(single wire) [DX1000]
R5F21292DSP@SOIC20(UART ISP) [DX0001]
R5F21292DSP@SOIC20(UART mode) [DX1000]
R5F21292JSP@SOIC20 [DX1000]
R5F21292JSP@SOIC20(single ISP) [DX0001]

R5F21292JSP@SOIC20(single wire) [DX1000]
R5F21292JSP@SOIC20(UART ISP) [DX0001]
R5F21292JSP@SOIC20(UART mode) [DX1000]
R5F21292KSP@SOIC20 [DX1000]
R5F21292KSP@SOIC20(single ISP) [DX0001]
R5F21292KSP@SOIC20(single wire) [DX1000]
R5F21292KSP@SOIC20(UART ISP) [DX0001]
R5F21292KSP@SOIC20(UART mode) [DX1000]
R5F21292NSP@SOIC20 [DX1000]
R5F21292NSP@SOIC20(single ISP) [DX0001]
R5F21292NSP@SOIC20(single wire) [DX1000]
R5F21292NSP@SOIC20(UART ISP) [DX0001]
R5F21292NSP@SOIC20(UART mode) [DX1000]
R5F21292SDSP@SOIC20 [DX1000]
R5F21292SDSP@SOIC20(single ISP) [DX0001]
R5F21292SDSP@SOIC20(single wire) [DX1000]
R5F21292SDSP@SOIC20(UART ISP) [DX0001]
R5F21292SDSP@SOIC20(UART mode) [DX1000]
R5F21292SJSP@SOIC20 [DX1000]
R5F21292SJSP@SOIC20(single ISP) [DX0001]
R5F21292SJSP@SOIC20(single wire) [DX1000]
R5F21292SJSP@SOIC20(UART ISP) [DX0001]
R5F21292SJSP@SOIC20(UART mode) [DX1000]
R5F21292SKSP@SOIC20 [DX1000]
R5F21292SKSP@SOIC20(single ISP) [DX0001]
R5F21292SKSP@SOIC20(single wire) [DX1000]
R5F21292SKSP@SOIC20(UART ISP) [DX0001]
R5F21292SKSP@SOIC20(UART mode) [DX1000]
R5F21292SNSP@SOIC20 [DX1000]
R5F21292SNSP@SOIC20(single ISP) [DX0001]
R5F21292SNSP@SOIC20(single wire) [DX1000]
R5F21292SNSP@SOIC20(UART ISP) [DX0001]
R5F21292SNSP@SOIC20(UART mode) [DX1000]
R5F21294DSP@SOIC20 [DX1000]
R5F21294DSP@SOIC20(single ISP) [DX0001]
R5F21294DSP@SOIC20(single wire) [DX1000]
R5F21294DSP@SOIC20(UART ISP) [DX0001]
R5F21294DSP@SOIC20(UART mode) [DX1000]
R5F21294JSP@SOIC20 [DX1000]
R5F21294JSP@SOIC20(single ISP) [DX0001]
R5F21294JSP@SOIC20(single wire) [DX1000]
R5F21294JSP@SOIC20(UART ISP) [DX0001]
R5F21294JSP@SOIC20(UART mode) [DX1000]
R5F21294KSP@SOIC20 [DX1000]
R5F21294KSP@SOIC20(single ISP) [DX0001]
R5F21294KSP@SOIC20(single wire) [DX1000]
R5F21294KSP@SOIC20(UART ISP) [DX0001]
R5F21294KSP@SOIC20(UART mode) [DX1000]

R5F21294NSP@SOIC20 [DX1000]
R5F21294NSP@SOIC20(single ISP) [DX0001]
R5F21294NSP@SOIC20(single wire) [DX1000]
R5F21294NSP@SOIC20(UART ISP) [DX0001]
R5F21294NSP@SOIC20(UART mode) [DX1000]
R5F21294SDSP@SOIC20 [DX1000]
R5F21294SDSP@SOIC20(single ISP) [DX0001]
R5F21294SDSP@SOIC20(single wire) [DX1000]
R5F21294SDSP@SOIC20(UART ISP) [DX0001]
R5F21294SDSP@SOIC20(UART mode) [DX1000]
R5F21294SJSP@SOIC20 [DX1000]
R5F21294SJSP@SOIC20(single ISP) [DX0001]
R5F21294SJSP@SOIC20(single wire) [DX1000]
R5F21294SJSP@SOIC20(UART ISP) [DX0001]
R5F21294SJSP@SOIC20(UART mode) [DX1000]
R5F21294SKSP@SOIC20 [DX1000]
R5F21294SKSP@SOIC20(single ISP) [DX0001]
R5F21294SKSP@SOIC20(single wire) [DX1000]
R5F21294SKSP@SOIC20(UART ISP) [DX0001]
R5F21294SKSP@SOIC20(UART mode) [DX1000]
R5F21294SNSP@SOIC20 [DX1000]
R5F21294SNSP@SOIC20(single ISP) [DX0001]
R5F21294SNSP@SOIC20(single wire) [DX1000]
R5F21294SNSP@SOIC20(UART ISP) [DX0001]
R5F21294SNSP@SOIC20(UART mode) [DX1000]
R5F212A7SDFA@TQFP64 [DX3044]
R5F212A7SDFA@TQFP64(single ISP) [DX0001]
R5F212A7SDFA@TQFP64(single wire) [DX3013]
R5F212A7SDFA@TQFP64(UART ISP) [DX0001]
R5F212A7SDFA@TQFP64(UART mode) [DX3013]
R5F212A7SDFP@TQFP64 [DX3011]
R5F212A7SDFP@TQFP64(single ISP) [DX0001]
R5F212A7SDFP@TQFP64(single wire) [DX3011]
R5F212A7SDFP@TQFP64(UART ISP) [DX0001]
R5F212A7SDFP@TQFP64(UART mode) [DX3011]
R5F212A7SNFA@TQFP64 [DX3044]
R5F212A7SNFA@TQFP64(single ISP) [DX0001]
R5F212A7SNFA@TQFP64(single wire) [DX3013]
R5F212A7SNFA@TQFP64(UART ISP) [DX0001]
R5F212A7SNFA@TQFP64(UART mode) [DX3013]
R5F212A7SNFP@TQFP64 [DX3011]
R5F212A7SNFP@TQFP64(single ISP) [DX0001]
R5F212A7SNFP@TQFP64(single wire) [DX3011]
R5F212A7SNFP@TQFP64(UART ISP) [DX0001]
R5F212A7SNFP@TQFP64(UART mode) [DX3011]
R5F212A8SDFA@TQFP64 [DX3044]
R5F212A8SDFA@TQFP64(single ISP) [DX0001]
R5F212A8SDFA@TQFP64(single wire) [DX3013]

R5F212A8SDFA@TQFP64(UART ISP) [DX0001]
R5F212A8SDFA@TQFP64(UART mode) [DX3013]
R5F212A8SDFP@TQFP64 [DX3011]
R5F212A8SDFP@TQFP64(single ISP) [DX0001]
R5F212A8SDFP@TQFP64(single wire) [DX3011]
R5F212A8SDFP@TQFP64(UART ISP) [DX0001]
R5F212A8SDFP@TQFP64(UART mode) [DX3011]
R5F212A8SNFA@TQFP64 [DX3044]
R5F212A8SNFA@TQFP64(single ISP) [DX0001]
R5F212A8SNFA@TQFP64(single wire) [DX3013]
R5F212A8SNFA@TQFP64(UART ISP) [DX0001]
R5F212A8SNFA@TQFP64(UART mode) [DX3013]
R5F212A8SNFP@TQFP64 [DX3011]
R5F212A8SNFP@TQFP64(single ISP) [DX0001]
R5F212A8SNFP@TQFP64(single wire) [DX3011]
R5F212A8SNFP@TQFP64(UART ISP) [DX0001]
R5F212A8SNFP@TQFP64(UART mode) [DX3011]
R5F212AASDFA@TQFP64 [DX3044]
R5F212AASDFA@TQFP64(single ISP) [DX0001]
R5F212AASDFA@TQFP64(single wire) [DX3013]
R5F212AASDFA@TQFP64(UART ISP) [DX0001]
R5F212AASDFA@TQFP64(UART mode) [DX3013]
R5F212AASDFP@TQFP64 [DX3011]
R5F212AASDFP@TQFP64(single ISP) [DX0001]
R5F212AASDFP@TQFP64(single wire) [DX3011]
R5F212AASDFP@TQFP64(UART ISP) [DX0001]
R5F212AASDFP@TQFP64(UART mode) [DX3011]
R5F212AASNFA@TQFP64 [DX3044]
R5F212AASNFA@TQFP64(single ISP) [DX0001]
R5F212AASNFA@TQFP64(single wire) [DX3013]
R5F212AASNFA@TQFP64(UART ISP) [DX0001]
R5F212AASNFA@TQFP64(UART mode) [DX3013]
R5F212AASNFP@TQFP64 [DX3011]
R5F212AASNFP@TQFP64(single ISP) [DX0001]
R5F212AASNFP@TQFP64(single wire) [DX3011]
R5F212AASNFP@TQFP64(UART ISP) [DX0001]
R5F212AASNFP@TQFP64(UART mode) [DX3011]
R5F212ACSDFA@TQFP64 [DX3044]
R5F212ACSDFA@TQFP64(single ISP) [DX0001]
R5F212ACSDFA@TQFP64(single wire) [DX3013]
R5F212ACSDFA@TQFP64(UART ISP) [DX0001]
R5F212ACSDFA@TQFP64(UART mode) [DX3013]
R5F212ACSDFP@TQFP64 [DX3011]
R5F212ACSDFP@TQFP64(single ISP) [DX0001]
R5F212ACSDFP@TQFP64(single wire) [DX3011]
R5F212ACSDFP@TQFP64(UART ISP) [DX0001]
R5F212ACSDFP@TQFP64(UART mode) [DX3011]
R5F212ACSNFA@TQFP64 [DX3044]

R5F212ACSNFA@TQFP64(single ISP) [DX0001]
R5F212ACSNFA@TQFP64(single wire) [DX3013]
R5F212ACSNFA@TQFP64(UART ISP) [DX0001]
R5F212ACSNFA@TQFP64(UART mode) [DX3013]
R5F212ACSNFP@TQFP64 [DX3011]
R5F212ACSNFP@TQFP64(single ISP) [DX0001]
R5F212ACSNFP@TQFP64(single wire) [DX3011]
R5F212ACSNFP@TQFP64(UART ISP) [DX0001]
R5F212ACSNFP@TQFP64(UART mode) [DX3011]
R5F212B7SDFA@TQFP64 [DX3044]
R5F212B7SDFA@TQFP64(single ISP) [DX0001]
R5F212B7SDFA@TQFP64(single wire) [DX3013]
R5F212B7SDFA@TQFP64(UART ISP) [DX0001]
R5F212B7SDFA@TQFP64(UART mode) [DX3013]
R5F212B7SDFP@TQFP64 [DX3011]
R5F212B7SDFP@TQFP64(single ISP) [DX0001]
R5F212B7SDFP@TQFP64(single wire) [DX3011]
R5F212B7SDFP@TQFP64(UART ISP) [DX0001]
R5F212B7SDFP@TQFP64(UART mode) [DX3011]
R5F212B7SNFA@TQFP64 [DX3044]
R5F212B7SNFA@TQFP64(single ISP) [DX0001]
R5F212B7SNFA@TQFP64(single wire) [DX3013]
R5F212B7SNFA@TQFP64(UART ISP) [DX0001]
R5F212B7SNFA@TQFP64(UART mode) [DX3013]
R5F212B7SNFP@TQFP64 [DX3011]
R5F212B7SNFP@TQFP64(single ISP) [DX0001]
R5F212B7SNFP@TQFP64(single wire) [DX3011]
R5F212B7SNFP@TQFP64(UART ISP) [DX0001]
R5F212B7SNFP@TQFP64(UART mode) [DX3011]
R5F212B8SDFA@TQFP64 [DX3044]
R5F212B8SDFA@TQFP64(single ISP) [DX0001]
R5F212B8SDFA@TQFP64(single wire) [DX3013]
R5F212B8SDFA@TQFP64(UART ISP) [DX0001]
R5F212B8SDFA@TQFP64(UART mode) [DX3013]
R5F212B8SDFP@TQFP64 [DX3011]
R5F212B8SDFP@TQFP64(single ISP) [DX0001]
R5F212B8SDFP@TQFP64(single wire) [DX3011]
R5F212B8SDFP@TQFP64(UART ISP) [DX0001]
R5F212B8SDFP@TQFP64(UART mode) [DX3011]
R5F212B8SNFA@TQFP64 [DX3044]
R5F212B8SNFA@TQFP64(single ISP) [DX0001]
R5F212B8SNFA@TQFP64(single wire) [DX3013]
R5F212B8SNFA@TQFP64(UART ISP) [DX0001]
R5F212B8SNFA@TQFP64(UART mode) [DX3013]
R5F212B8SNFP@TQFP64 [DX3011]
R5F212B8SNFP@TQFP64(single ISP) [DX0001]
R5F212B8SNFP@TQFP64(single wire) [DX3011]
R5F212B8SNFP@TQFP64(UART ISP) [DX0001]

R5F212B8SNFP@TQFP64(UART mode) [DX3011]
R5F212BASDFA@TQFP64 [DX3044]
R5F212BASDFA@TQFP64(single ISP) [DX0001]
R5F212BASDFA@TQFP64(single wire) [DX3013]
R5F212BASDFA@TQFP64(UART ISP) [DX0001]
R5F212BASDFA@TQFP64(UART mode) [DX3013]
R5F212BASDFP@TQFP64 [DX3011]
R5F212BASDFP@TQFP64(single ISP) [DX0001]
R5F212BASDFP@TQFP64(single wire) [DX3011]
R5F212BASDFP@TQFP64(UART ISP) [DX0001]
R5F212BASDFP@TQFP64(UART mode) [DX3011]
R5F212BASNFA@TQFP64 [DX3044]
R5F212BASNFA@TQFP64(single ISP) [DX0001]
R5F212BASNFA@TQFP64(single wire) [DX3013]
R5F212BASNFA@TQFP64(UART ISP) [DX0001]
R5F212BASNFA@TQFP64(UART mode) [DX3013]
R5F212BASNFP@TQFP64 [DX3011]
R5F212BASNFP@TQFP64(single ISP) [DX0001]
R5F212BASNFP@TQFP64(single wire) [DX3011]
R5F212BASNFP@TQFP64(UART ISP) [DX0001]
R5F212BASNFP@TQFP64(UART mode) [DX3011]
R5F212BCSDFA@TQFP64 [DX3044]
R5F212BCSDFA@TQFP64(single ISP) [DX0001]
R5F212BCSDFA@TQFP64(single wire) [DX3013]
R5F212BCSDFA@TQFP64(UART ISP) [DX0001]
R5F212BCSDFA@TQFP64(UART mode) [DX3013]
R5F212BCSDFP@TQFP64 [DX3011]
R5F212BCSDFP@TQFP64(single ISP) [DX0001]
R5F212BCSDFP@TQFP64(single wire) [DX3011]
R5F212BCSDFP@TQFP64(UART ISP) [DX0001]
R5F212BCSDFP@TQFP64(UART mode) [DX3011]
R5F212BCSNFA@TQFP64 [DX3044]
R5F212BCSNFA@TQFP64(single ISP) [DX0001]
R5F212BCSNFA@TQFP64(single wire) [DX3013]
R5F212BCSNFA@TQFP64(UART ISP) [DX0001]
R5F212BCSNFA@TQFP64(UART mode) [DX3013]
R5F212BCSNFP@TQFP64 [DX3011]
R5F212BCSNFP@TQFP64(single ISP) [DX0001]
R5F212BCSNFP@TQFP64(single wire) [DX3011]
R5F212BCSNFP@TQFP64(UART ISP) [DX0001]
R5F212BCSNFP@TQFP64(UART mode) [DX3011]
R5F212C7SDFP@TQFP80 [DX3016]
R5F212C7SDFP@TQFP80(single ISP) [DX0001]
R5F212C7SDFP@TQFP80(single wire) [DX3016]
R5F212C7SDFP@TQFP80(UART ISP) [DX0001]
R5F212C7SDFP@TQFP80(UART mode) [DX3016]
R5F212C7SNFP@TQFP80 [DX3016]
R5F212C7SNFP@TQFP80(single ISP) [DX0001]

R5F212C7SNFP@TQFP80(single wire) [DX3016]
R5F212C7SNFP@TQFP80(UART ISP) [DX0001]
R5F212C7SNFP@TQFP80(UART mode) [DX3016]
R5F212C8SDFP@TQFP80 [DX3016]
R5F212C8SDFP@TQFP80(single ISP) [DX0001]
R5F212C8SDFP@TQFP80(single wire) [DX3016]
R5F212C8SDFP@TQFP80(UART ISP) [DX0001]
R5F212C8SDFP@TQFP80(UART mode) [DX3016]
R5F212C8SNFP@TQFP80 [DX3016]
R5F212C8SNFP@TQFP80(single ISP) [DX0001]
R5F212C8SNFP@TQFP80(single wire) [DX3016]
R5F212C8SNFP@TQFP80(UART ISP) [DX0001]
R5F212C8SNFP@TQFP80(UART mode) [DX3016]
R5F212CASDFP@TQFP80 [DX3016]
R5F212CASDFP@TQFP80(single ISP) [DX0001]
R5F212CASDFP@TQFP80(single wire) [DX3016]
R5F212CASDFP@TQFP80(UART ISP) [DX0001]
R5F212CASDFP@TQFP80(UART mode) [DX3016]
R5F212CASNFP@TQFP80 [DX3016]
R5F212CASNFP@TQFP80(single ISP) [DX0001]
R5F212CASNFP@TQFP80(single wire) [DX3016]
R5F212CASNFP@TQFP80(UART ISP) [DX0001]
R5F212CASNFP@TQFP80(UART mode) [DX3016]
R5F212CCSDFP@TQFP80 [DX3016]
R5F212CCSDFP@TQFP80(single ISP) [DX0001]
R5F212CCSDFP@TQFP80(single wire) [DX3016]
R5F212CCSDFP@TQFP80(UART ISP) [DX0001]
R5F212CCSDFP@TQFP80(UART mode) [DX3016]
R5F212CCSNFP@TQFP80 [DX3016]
R5F212CCSNFP@TQFP80(single ISP) [DX0001]
R5F212CCSNFP@TQFP80(single wire) [DX3016]
R5F212CCSNFP@TQFP80(UART ISP) [DX0001]
R5F212CCSNFP@TQFP80(UART mode) [DX3016]
R5F212D7SDFP@TQFP80 [DX3016]
R5F212D7SDFP@TQFP80(single ISP) [DX0001]
R5F212D7SDFP@TQFP80(single wire) [DX3016]
R5F212D7SDFP@TQFP80(UART ISP) [DX0001]
R5F212D7SDFP@TQFP80(UART mode) [DX3016]
R5F212D7SNFP@TQFP80 [DX3016]
R5F212D7SNFP@TQFP80(single ISP) [DX0001]
R5F212D7SNFP@TQFP80(single wire) [DX3016]
R5F212D7SNFP@TQFP80(UART ISP) [DX0001]
R5F212D7SNFP@TQFP80(UART mode) [DX3016]
R5F212D8SDFP@TQFP80 [DX3016]
R5F212D8SDFP@TQFP80(single ISP) [DX0001]
R5F212D8SDFP@TQFP80(single wire) [DX3016]
R5F212D8SDFP@TQFP80(UART ISP) [DX0001]
R5F212D8SDFP@TQFP80(UART mode) [DX3016]

R5F212D8SNFP@TQFP80 [DX3016]
R5F212D8SNFP@TQFP80(single ISP) [DX0001]
R5F212D8SNFP@TQFP80(single wire) [DX3016]
R5F212D8SNFP@TQFP80(UART ISP) [DX0001]
R5F212D8SNFP@TQFP80(UART mode) [DX3016]
R5F212DASDFP@TQFP80 [DX3016]
R5F212DASDFP@TQFP80(single ISP) [DX0001]
R5F212DASDFP@TQFP80(single wire) [DX3016]
R5F212DASDFP@TQFP80(UART ISP) [DX0001]
R5F212DASDFP@TQFP80(UART mode) [DX3016]
R5F212DASNFP@TQFP80 [DX3016]
R5F212DASNFP@TQFP80(single ISP) [DX0001]
R5F212DASNFP@TQFP80(single wire) [DX3016]
R5F212DASNFP@TQFP80(UART ISP) [DX0001]
R5F212DASNFP@TQFP80(UART mode) [DX3016]
R5F212DCSDFP@TQFP80 [DX3016]
R5F212DCSDFP@TQFP80(single ISP) [DX0001]
R5F212DCSDFP@TQFP80(single wire) [DX3016]
R5F212DCSDFP@TQFP80(UART ISP) [DX0001]
R5F212DCSDFP@TQFP80(UART mode) [DX3016]
R5F212DCSNFP@TQFP80 [DX3016]
R5F212DCSNFP@TQFP80(single ISP) [DX0001]
R5F212DCSNFP@TQFP80(single wire) [DX3016]
R5F212DCSNFP@TQFP80(UART ISP) [DX0001]
R5F212DCSNFP@TQFP80(UART mode) [DX3016]
R5F212G4SDFP@QFP32 [DX3061]
R5F212G4SDFP@QFP32(single ISP) [DX0001]
R5F212G4SDFP@QFP32(single wire) [DX3061]
R5F212G4SNFP@QFP32 [DX3061]
R5F212G4SNFP@QFP32(single ISP) [DX0001]
R5F212G4SNFP@QFP32(single wire) [DX3061]
R5F212G5SDFP@QFP32 [DX3061]
R5F212G5SDFP@QFP32(single ISP) [DX0001]
R5F212G5SDFP@QFP32(single wire) [DX3061]
R5F212G5SNFP@QFP32 [DX3061]
R5F212G5SNFP@QFP32(single ISP) [DX0001]
R5F212G5SNFP@QFP32(single wire) [DX3061]
R5F212G6SDFP@QFP32 [DX3061]
R5F212G6SDFP@QFP32(single ISP) [DX0001]
R5F212G6SDFP@QFP32(single wire) [DX3061]
R5F212G6SNFP@QFP32 [DX3061]
R5F212G6SNFP@QFP32(single ISP) [DX0001]
R5F212G6SNFP@QFP32(single wire) [DX3061]
R5F212H1SDSP@TSSOP20 [DX1000]
R5F212H1SDSP@TSSOP20(single ISP) [DX0001]
R5F212H1SDSP@TSSOP20(single) [DX1000]
R5F212H1SNSP@TSSOP20 [DX1000]
R5F212H1SNSP@TSSOP20(single ISP) [DX0001]

R5F212H1SNSP@TSSOP20(single) [DX1000]
R5F212H2SDSP@TSSOP20 [DX1000]
R5F212H2SDSP@TSSOP20(single ISP) [DX0001]
R5F212H2SDSP@TSSOP20(single) [DX1000]
R5F212H2SNSP@TSSOP20 [DX1000]
R5F212H2SNSP@TSSOP20(single ISP) [DX0001]
R5F212H2SNSP@TSSOP20(single) [DX1000]
R5F212J0SDSP@TSSOP20 [DX1000]
R5F212J0SDSP@TSSOP20(single ISP) [DX0001]
R5F212J0SDSP@TSSOP20(single) [DX1000]
R5F212J0SNSP@TSSOP20 [DX1000]
R5F212J0SNSP@TSSOP20(single ISP) [DX0001]
R5F212J0SNSP@TSSOP20(single) [DX1000]
R5F212J1SDSP@TSSOP20 [DX1000]
R5F212J1SDSP@TSSOP20(single ISP) [DX0001]
R5F212J1SDSP@TSSOP20(single) [DX1000]
R5F212J1SNSP@TSSOP20 [DX1000]
R5F212J1SNSP@TSSOP20(single ISP) [DX0001]
R5F212J1SNSP@TSSOP20(single) [DX1000]
R5F212K2SDFP@QFP32 [DX3061]
R5F212K2SDFP@QFP32(single ISP) [DX0001]
R5F212K2SDFP@QFP32(single wire) [DX3050]
R5F212K2SDFP@QFP32(UART ISP) [DX0001]
R5F212K2SDFP@QFP32(UART mode) [DX3050]
R5F212K2SNFP@QFP32 [DX3061]
R5F212K2SNFP@QFP32(single ISP) [DX0001]
R5F212K2SNFP@QFP32(single wire) [DX3050]
R5F212K2SNFP@QFP32(UART ISP) [DX0001]
R5F212K2SNFP@QFP32(UART mode) [DX3050]
R5F212K4SDFP@QFP32 [DX3061]
R5F212K4SDFP@QFP32(single ISP) [DX0001]
R5F212K4SDFP@QFP32(single wire) [DX3050]
R5F212K4SDFP@QFP32(UART ISP) [DX0001]
R5F212K4SDFP@QFP32(UART mode) [DX3050]
R5F212K4SNFP@QFP32 [DX3061]
R5F212K4SNFP@QFP32(single ISP) [DX0001]
R5F212K4SNFP@QFP32(single wire) [DX3050]
R5F212K4SNFP@QFP32(UART ISP) [DX0001]
R5F212K4SNFP@QFP32(UART mode) [DX3050]
R5F212L2SDFP@QFP32 [DX3061]
R5F212L2SDFP@QFP32(single ISP) [DX0001]
R5F212L2SDFP@QFP32(single wire) [DX3050]
R5F212L2SDFP@QFP32(UART ISP) [DX0001]
R5F212L2SDFP@QFP32(UART mode) [DX3050]
R5F212L2SNFP@QFP32 [DX3061]
R5F212L2SNFP@QFP32(single ISP) [DX0001]
R5F212L2SNFP@QFP32(single wire) [DX3050]
R5F212L2SNFP@QFP32(UART ISP) [DX0001]

R5F212L2SNFP@QFP32(UART mode) [DX3050]
R5F212L4SDFP@QFP32 [DX3061]
R5F212L4SDFP@QFP32(single ISP) [DX0001]
R5F212L4SDFP@QFP32(single wire) [DX3050]
R5F212L4SDFP@QFP32(UART ISP) [DX0001]
R5F212L4SDFP@QFP32(UART mode) [DX3050]
R5F212L4SNFP@QFP32 [DX3061]
R5F212L4SNFP@QFP32(single ISP) [DX0001]
R5F212L4SNFP@QFP32(single wire) [DX3050]
R5F212L4SNFP@QFP32(UART ISP) [DX0001]
R5F212L4SNFP@QFP32(UART mode) [DX3050]
R5F21331ADFP [DX3001]
R5F21331ANFP [DX3001]
R5F21331CDFP [DX3001]
R5F21331CNFP [DX3001]
R5F21331DDFP [DX3001]
R5F21331DNFP [DX3001]
R5F21331MDFP [DX3001]
R5F21331MNFP [DX3001]
R5F21332ADFP [DX3001]
R5F21332ANFP [DX3001]
R5F21332CDFP [DX3001]
R5F21332CNFP [DX3001]
R5F21332DDFP [DX3001]
R5F21332DNFP [DX3001]
R5F21332MDFP [DX3001]
R5F21332MNFP [DX3001]
R5F21334ADFP [DX3001]
R5F21334ANFP [DX3001]
R5F21334CDFP [DX3001]
R5F21334CNFP [DX3001]
R5F21334DDFP [DX3001]
R5F21334DNFP [DX3001]
R5F21334MDFP [DX3001]
R5F21334MNFP [DX3001]
R5F21334TDFP [DX3001]
R5F21334TNFP [DX3001]
R5F21335ADFP [DX3001]
R5F21335ANFP [DX3001]
R5F21335CDFP [DX3001]
R5F21335CNFP [DX3001]
R5F21335DDFP [DX3001]
R5F21335DNFP [DX3001]
R5F21335MDFP [DX3001]
R5F21335MNFP [DX3001]
R5F21335TDFP [DX3001]
R5F21335TNFP [DX3001]
R5F21336ADFP [DX3001]
R5F21336ANFP [DX3001]
R5F21336CDFP [DX3001]
R5F21336CNFP [DX3001]
R5F21336DDFP [DX3001]
R5F21336DNFP [DX3001]
R5F21336MDFP [DX3001]
R5F21336MNFP [DX3001]
R5F21336MYFP@QFP32 [DX3001]
R5F21336TDFP [DX3001]
R5F21336TNFP [DX3001]
R5F21346EJFP@QFP48 [DX3007]
R5F21346EKFP@QFP48 [DX3007]
R5F21346FJFP@QFP48 [DX3007]
R5F21346FKFP@QFP48 [DX3007]
R5F21346GJFP@QFP48 [DX3007]
R5F21346GKFP@QFP48 [DX3007]
R5F21346HJFP@QFP48 [DX3007]
R5F21346HKFP@QFP48 [DX3007]
R5F21346WJFP [DX3007]
R5F21346WKFP [DX3007]
R5F21347EJFP@QFP48 [DX3007]
R5F21347EKFP@QFP48 [DX3007]
R5F21347FJFP@QFP48 [DX3007]
R5F21347FKFP@QFP48 [DX3007]
R5F21347GJFP@QFP48 [DX3007]
R5F21347GKFP@QFP48 [DX3007]
R5F21347HJFP@QFP48 [DX3007]
R5F21347HKFP@QFP48 [DX3007]
R5F21347WJFP [DX3007]
R5F21347WKFP [DX3007]
R5F21348EJFP@QFP48 [DX3007]
R5F21348EKFP@QFP48 [DX3007]
R5F21348FJFP@QFP48 [DX3007]
R5F21348FKFP@QFP48 [DX3007]
R5F21348GJFP@QFP48 [DX3007]
R5F21348GKFP@QFP48 [DX3007]
R5F21348HJFP@QFP48 [DX3007]

R5F21348HKFP@QFP48 [DX3007]
R5F21348WJFP [DX3007]
R5F21348WKFP [DX3007]
R5F2134AEJFP@QFP48 [DX3007]
R5F2134AEKFP@QFP48 [DX3007]
R5F2134AFJFP@QFP48 [DX3007]
R5F2134AFKFP@QFP48 [DX3007]
R5F2134AGJFP@QFP48 [DX3007]
R5F2134AGKFP@QFP48 [DX3007]
R5F2134AHJFP@QFP48 [DX3007]
R5F2134AHKFP@QFP48 [DX3007]
R5F2134AWJFP [DX3007]
R5F2134AWKFP [DX3007]
R5F2134CEJFP@QFP48 [DX3007]
R5F2134CEKFP@QFP48 [DX3007]
R5F2134CFJFP@QFP48 [DX3007]
R5F2134CFKFP@QFP48 [DX3007]
R5F2134CGJFP@QFP48 [DX3007]
R5F2134CGKFP@QFP48 [DX3007]
R5F2134CHJFP@QFP48 [DX3007]
R5F2134CHKFP@QFP48 [DX3007]
R5F2134CWJFP [DX3007]
R5F2134CWKFP@QFP48 [DX3007]
R5F2134CWKFP@QFP48(left down) [DX3007]
R5F21354ADFP [DX3010]
R5F21354ADFP@QFP52(single wire) [DX3010]
R5F21354ANFP [DX3010]
R5F21354ANFP@QFP52(single wire) [DX3010]
R5F21354BDFP@QFP52(single wire) [DX3010]
R5F21354BNFP@QFP52(single wire) [DX3010]
R5F21354CDFP [DX3010]
R5F21354CDFP@QFP52(single wire) [DX3010]
R5F21354CNFP [DX3010]
R5F21354CNFP@QFP52(single wire) [DX3010]
R5F21354CYFP [DX3010]
R5F21354MDFP [DX3010]
R5F21354MNFP [DX3010]
R5F21355ADFP [DX3010]
R5F21355ADFP@QFP52(single wire) [DX3010]
R5F21355ANFP [DX3010]
R5F21355ANFP@QFP52(single wire) [DX3010]
R5F21355BDFP@QFP52(single wire) [DX3010]
R5F21355BNFP@QFP52(single wire) [DX3010]
R5F21355CDFP [DX3010]
R5F21355CDFP@QFP52(single wire) [DX3010]
R5F21355CNFP [DX3010]
R5F21355CNFP@QFP52(single wire) [DX3010]
R5F21355CYFP [DX3010]
R5F21355MDFP [DX3010]
R5F21355MNFP [DX3010]
R5F21356ADFP [DX3010]
R5F21356ADFP@QFP52(single wire) [DX3010]
R5F21356ANFP [DX3010]
R5F21356ANFP@QFP52(single wire) [DX3010]
R5F21356BDFP@QFP52(single wire) [DX3010]
R5F21356BNFP@QFP52(single wire) [DX3010]
R5F21356CDFP [DX3010]
R5F21356CDFP@QFP52(single wire) [DX3010]
R5F21356CNFP [DX3010]
R5F21356CNFP@QFP52(single wire) [DX3010]
R5F21356CYFP [DX3010]
R5F21356MDFP [DX3010]
R5F21356MNFP [DX3010]
R5F21357ADFP [DX3010]
R5F21357ADFP@QFP52(single wire) [DX3010]

R5F21357ANFP [DX3010]
R5F21357ANFP@QFP52(single wire) [DX3010]
R5F21357BDFP@QFP52(single wire) [DX3010]
R5F21357BNFP@QFP52(single wire) [DX3010]
R5F21357CDFP [DX3010]
R5F21357CDFP@QFP52(single wire) [DX3010]
R5F21357CNFP [DX3010]
R5F21357CNFP@QFP52(single wire) [DX3010]
R5F21357CYFP [DX3010]
R5F21357CYFP@QFP52(single wire) [DX3010]
R5F21357MDFP [DX3010]　　R5F21357MNFP [DX3010]
R5F21358ADFP [DX3010]
R5F21358ADFP@QFP52(single wire) [DX3010]
R5F21358ANFP [DX3010]
R5F21358ANFP@QFP52(single wire) [DX3010]
R5F21358BDFP@QFP52(single wire) [DX3010]
R5F21358BNFP@QFP52(single wire) [DX3010]
R5F21358CDFP [DX3010]
R5F21358CDFP@QFP52(single wire) [DX3010]
R5F21358CNFP [DX3010]
R5F21358CNFP@QFP52(single wire) [DX3010]
R5F21358CYFP [DX3010]　　R5F21358MDFP [DX3010]
R5F21358MNFP [DX3010]　　R5F2135AADFP [DX3010]
R5F2135AADFP@QFP52(single wire) [DX3010]
R5F2135AANFP [DX3010]
R5F2135AANFP@QFP52(single wire) [DX3010]
R5F2135ABDFP@QFP52(single wire) [DX3010]
R5F2135ABNFP@QFP52(single wire) [DX3010]
R5F2135ACDFP [DX3010]
R5F2135ACDFP@QFP52(single wire) [DX3010]
R5F2135ACNFP [DX3010]
R5F2135ACNFP@QFP52(single wire) [DX3010]
R5F2135ACYFP [DX3010]　　R5F2135AMDFP [DX3010]
R5F2135AMNFP [DX3010]　　R5F2135CADFP [DX3010]
R5F2135CADFP@QFP52(single wire) [DX3010]
R5F2135CANFP [DX3010]
R5F2135CANFP@QFP52(single wire) [DX3010]
R5F2135CBDFP@QFP52(single wire) [DX3010]
R5F2135CBNFP@QFP52(single wire) [DX3010]
R5F2135CCDFP [DX3010]
R5F2135CCDFP@QFP52(single wire) [DX3010]
R5F2135CCNFP [DX3010]
R5F2135CCNFP@QFP52(single wire) [DX3010]
R5F2135CCYFP [DX3010]　　R5F2135CMDFP [DX3010]
R5F2135CMNFP [DX3010]　　R5F21364ADFA [DX3100]
R5F21364ADFP [DX3011]　　R5F21364ANFA [DX3100]
R5F21364ANFP [DX3011]　　R5F21364CDFA [DX3100]
R5F21364CDFP [DX3011]　　R5F21364CNFA [DX3100]

R5F21364CNFP [DX3011]
R5F21365ADFP [DX3011]
R5F21365ANFP [DX3011]
R5F21365CDFP [DX3011]
R5F21365CNFP [DX3011]
R5F21366ADFP [DX3011]
R5F21366ANFP [DX3011]
R5F21366CDFP [DX3011]
R5F21366CNFP [DX3011]
R5F21367ADFP [DX3011]
R5F21367ANFP [DX3011]
R5F21367CDFP [DX3011]
R5F21367CNFP [DX3011]
R5F21368ADFP [DX3011]
R5F21368ANFP [DX3011]
R5F21368CDFP [DX3011]
R5F21368CNFP [DX3011]
R5F2136AADFP [DX3011]
R5F2136AANFP [DX3011]
R5F2136ACDFP [DX3011]
R5F2136ACNFP [DX3011]
R5F2136CADFP [DX3011]
R5F2136CANFP [DX3011]
R5F2136CCDFP [DX3011]
R5F2136CCNFP [DX3011]
R5F213G1DNSP [DX1095]
R5F213G2DNSP [DX1095]
R5F213G4DNSP [DX1095]
R5F213G5DNSP [DX1095]
R5F213G6DNSP [DX1095]
R5F21365ADFA [DX3100]
R5F21365ANFA [DX3100]
R5F21365CDFA [DX3100]
R5F21365CNFA [DX3100]
R5F21366ADFA [DX3100]
R5F21366ANFA [DX3100]
R5F21366CDFA [DX3100]
R5F21366CNFA [DX3100]
R5F21367ADFA [DX3100]
R5F21367ANFA [DX3100]
R5F21367CDFA [DX3100]
R5F21367CNFA [DX3100]
R5F21368ADFA [DX3100]
R5F21368ANFA [DX3100]
R5F21368CDFA [DX3100]
R5F21368CNFA [DX3100]
R5F2136AADFA [DX3100]
R5F2136AANFA [DX3100]
R5F2136ACDFA [DX3100]
R5F2136ACNFA [DX3100]
R5F2136CADFA [DX3100]
R5F2136CANFA [DX3100]
R5F2136CCDFA [DX3100]
R5F2136CCNFA [DX3100]
R5F213G1DDSP [DX1095]
R5F213G2DDSP [DX1095]
R5F213G4DDSP [DX1095]
R5F213G5DDSP [DX1095]
R5F213G6DDSP [DX1095]
R5F2L357ADFP@QFP52 [DX3010]
R5F2L357ADFP@QFP52(single wire) [DX3010]
R5F2L357ANFP@QFP52 [DX3010]
R5F2L357ANFP@QFP52(single wire) [DX3010]
R5F2L357BDFP@QFP52 [DX3010]
R5F2L357BDFP@QFP52(single wire) [DX3010]
R5F2L357BNFP@QFP52 [DX3010]
R5F2L357BNFP@QFP52(single wire) [DX3010]
R5F2L357CDFP@QFP52 [DX3010]
R5F2L357CDFP@QFP52(single wire) [DX3010]
R5F2L357CNFP@QFP52 [DX3010]
R5F2L357CNFP@QFP52(single wire) [DX3010]
R5F2L358ADFP@QFP52 [DX3010]
R5F2L358ADFP@QFP52(single wire) [DX3010]
R5F2L358ANFP@QFP52 [DX3010]
R5F2L358ANFP@QFP52(single wire) [DX3010]
R5F2L358BDFP@QFP52 [DX3010]
R5F2L358BDFP@QFP52(single wire) [DX3010]
R5F2L358BNFP@QFP52 [DX3010]

R5F2L358BNFP@QFP52(single wire) [DX3010]
R5F2L358CDFP@QFP52 [DX3010]
R5F2L358CDFP@QFP52(single wire) [DX3010]
R5F2L358CNFP@QFP52 [DX3010]
R5F2L358CNFP@QFP52(single wire) [DX3010]
R5F2L35AADFP@QFP52 [DX3010]
R5F2L35AADFP@QFP52(single wire) [DX3010]
R5F2L35AANFP@QFP52 [DX3010]
R5F2L35AANFP@QFP52(single wire) [DX3010]
R5F2L35ABDFP@QFP52 [DX3010]
R5F2L35ABDFP@QFP52(single wire) [DX3010]
R5F2L35ABNFP@QFP52 [DX3010]
R5F2L35ABNFP@QFP52(single wire) [DX3010]
R5F2L35ACDFP@QFP52 [DX3010]
R5F2L35ACDFP@QFP52(single wire) [DX3010]
R5F2L35ACNFP@QFP52 [DX3010]
R5F2L35ACNFP@QFP52(single wire) [DX3010]
R5F2L35CADFP@QFP52 [DX3010]
R5F2L35CADFP@QFP52(single wire) [DX3010]
R5F2L35CANFP@QFP52 [DX3010]
R5F2L35CANFP@QFP52(single wire) [DX3010]
R5F2L35CBDFP@QFP52 [DX3010]
R5F2L35CBDFP@QFP52(single wire) [DX3010]
R5F2L35CBNFP@QFP52 [DX3010]
R5F2L35CBNFP@QFP52(single wire) [DX3010]
R5F2L35CCDFP@QFP52 [DX3010]
R5F2L35CCDFP@QFP52(single wire) [DX3010]
R5F2L35CCNFP@QFP52 [DX3010]
R5F2L35CCNFP@QFP52(single wire) [DX3010]
R5F2L367ADFA@QFP64 [DX3013]
R5F2L367ADFA@QFP64(single wire) [DX3013]
R5F2L367ADFP@QFP64 [DX3011]
R5F2L367ADFP@QFP64(single wire) [DX3011]
R5F2L367ANFA@QFP64 [DX3013]
R5F2L367ANFA@QFP64(single wire) [DX3013]
R5F2L367ANFP@QFP64 [DX3011]
R5F2L367ANFP@QFP64(single wire) [DX3011]
R5F2L367BDFA@QFP64 [DX3013]
R5F2L367BDFA@QFP64(single wire) [DX3013]
R5F2L367BDFP@QFP64 [DX3011]
R5F2L367BDFP@QFP64(single wire) [DX3011]
R5F2L367BNFA@QFP64 [DX3013]
R5F2L367BNFA@QFP64(single wire) [DX3013]
R5F2L367BNFP@QFP64 [DX3011]
R5F2L367BNFP@QFP64(single wire) [DX3011]
R5F2L367CDFA@QFP64 [DX3013]
R5F2L367CDFA@QFP64(single wire) [DX3013]
R5F2L367CDFP@QFP64 [DX3011]

R5F2L367CDFP@QFP64(single wire) [DX3011]
R5F2L367CNFA@QFP64 [DX3013]
R5F2L367CNFA@QFP64(single wire) [DX3013]
R5F2L367CNFP@QFP64 [DX3011]
R5F2L367CNFP@QFP64(single wire) [DX3011]
R5F2L368ADFA@QFP64 [DX3013]
R5F2L368ADFA@QFP64(single wire) [DX3013]
R5F2L368ADFP@QFP64 [DX3011]
R5F2L368ADFP@QFP64(single wire) [DX3011]
R5F2L368ANFA@QFP64 [DX3013]
R5F2L368ANFA@QFP64(single wire) [DX3013]
R5F2L368ANFP@QFP64 [DX3011]
R5F2L368ANFP@QFP64(single wire) [DX3011]
R5F2L368BDFA@QFP64 [DX3013]
R5F2L368BDFA@QFP64(single wire) [DX3013]
R5F2L368BDFP@QFP64 [DX3011]
R5F2L368BDFP@QFP64(single wire) [DX3011]
R5F2L368BNFA@QFP64 [DX3013]
R5F2L368BNFA@QFP64(single wire) [DX3013]
R5F2L368BNFP@QFP64 [DX3011]
R5F2L368BNFP@QFP64(single wire) [DX3011]
R5F2L368CDFA@QFP64 [DX3013]
R5F2L368CDFA@QFP64(single wire) [DX3013]
R5F2L368CDFP@QFP64 [DX3011]
R5F2L368CDFP@QFP64(single wire) [DX3011]
R5F2L368CNFA@QFP64 [DX3013]
R5F2L368CNFA@QFP64(single wire) [DX3013]
R5F2L368CNFP@QFP64 [DX3011]
R5F2L368CNFP@QFP64(single wire) [DX3011]
R5F2L36AADFA@QFP64 [DX3013]
R5F2L36AADFA@QFP64(single wire) [DX3013]
R5F2L36AADFP@QFP64 [DX3011]
R5F2L36AADFP@QFP64(single wire) [DX3011]
R5F2L36AANFA@QFP64 [DX3013]
R5F2L36AANFA@QFP64(single wire) [DX3013]
R5F2L36AANFP@QFP64 [DX3011]
R5F2L36AANFP@QFP64(single wire) [DX3011]
R5F2L36ABDFA@QFP64 [DX3013]
R5F2L36ABDFA@QFP64(single wire) [DX3013]
R5F2L36ABDFP@QFP64 [DX3011]
R5F2L36ABDFP@QFP64(single wire) [DX3011]
R5F2L36ABNFA@QFP64 [DX3013]
R5F2L36ABNFA@QFP64(single wire) [DX3013]
R5F2L36ABNFP@QFP64 [DX3011]
R5F2L36ABNFP@QFP64(single wire) [DX3011]
R5F2L36ACDFA@QFP64 [DX3013]
R5F2L36ACDFA@QFP64(single wire) [DX3013]
R5F2L36ACDFP@QFP64 [DX3011]

R5F2L36ACDFP@QFP64(single wire) [DX3011]
R5F2L36ACNFA@QFP64 [DX3013]
R5F2L36ACNFA@QFP64(single wire) [DX3013]
R5F2L36ACNFP@QFP64 [DX3011]
R5F2L36ACNFP@QFP64(single wire) [DX3011]
R5F2L36CADFA@QFP64 [DX3013]
R5F2L36CADFA@QFP64(single wire) [DX3013]
R5F2L36CADFP@QFP64 [DX3011]
R5F2L36CADFP@QFP64(single wire) [DX3011]
R5F2L36CANFA@QFP64 [DX3013]
R5F2L36CANFA@QFP64(single wire) [DX3013]
R5F2L36CANFP@QFP64 [DX3011]
R5F2L36CANFP@QFP64(single wire) [DX3011]
R5F2L36CBDFA@QFP64 [DX3013]
R5F2L36CBDFA@QFP64(single wire) [DX3013]
R5F2L36CBDFP@QFP64 [DX3011]
R5F2L36CBDFP@QFP64(single wire) [DX3011]
R5F2L36CBNFA@QFP64 [DX3013]
R5F2L36CBNFA@QFP64(single wire) [DX3013]
R5F2L36CBNFP@QFP64 [DX3011]
R5F2L36CBNFP@QFP64(single wire) [DX3011]
R5F2L36CCDFA@QFP64 [DX3013]
R5F2L36CCDFA@QFP64(single wire) [DX3013]
R5F2L36CCDFP@QFP64 [DX3011]
R5F2L36CCDFP@QFP64(single wire) [DX3011]
R5F2L36CCNFA@QFP64 [DX3013]
R5F2L36CCNFA@QFP64(single wire) [DX3013]
R5F2L36CCNFP@QFP64 [DX3011]
R5F2L36CCNFP@QFP64(single wire) [DX3011]
R5F2L387ADFA@QFP80 [DX3018]
R5F2L387ADFA@QFP80(single wire) [DX3018]
R5F2L387ADFP@QFP80 [DX3016]
R5F2L387ADFP@QFP80(single wire) [DX3016]
R5F2L387ANFA@QFP80 [DX3018]
R5F2L387ANFA@QFP80(single wire) [DX3018]
R5F2L387ANFP@QFP80 [DX3016]
R5F2L387ANFP@QFP80(single wire) [DX3016]
R5F2L387BDFA@QFP80 [DX3018]
R5F2L387BDFA@QFP80(single wire) [DX3018]
R5F2L387BDFP@QFP80 [DX3016]
R5F2L387BDFP@QFP80(single wire) [DX3016]
R5F2L387BNFA@QFP80 [DX3018]
R5F2L387BNFA@QFP80(single wire) [DX3018]
R5F2L387BNFP@QFP80 [DX3016]
R5F2L387BNFP@QFP80(single wire) [DX3016]
R5F2L387CDFA@QFP80 [DX3018]
R5F2L387CDFA@QFP80(single wire) [DX3018]
R5F2L387CDFP@QFP80 [DX3016]

R5F2L387CDFP@QFP80(single wire) [DX3016]
R5F2L387CNFA@QFP80 [DX3018]
R5F2L387CNFA@QFP80(single wire) [DX3018]
R5F2L387CNFP@QFP80 [DX3016]
R5F2L387CNFP@QFP80(single wire) [DX3016]
R5F2L388ADFA@QFP80 [DX3018]
R5F2L388ADFA@QFP80(single wire) [DX3018]
R5F2L388ADFP@QFP80 [DX3016]
R5F2L388ADFP@QFP80(single wire) [DX3016]
R5F2L388ANFA@QFP80 [DX3018]
R5F2L388ANFA@QFP80(single wire) [DX3018]
R5F2L388ANFP@QFP80 [DX3016]
R5F2L388ANFP@QFP80(single wire) [DX3016]
R5F2L388BDFA@QFP80 [DX3018]
R5F2L388BDFA@QFP80(single wire) [DX3018]
R5F2L388BDFP@QFP80 [DX3016]
R5F2L388BDFP@QFP80(single wire) [DX3016]
R5F2L388BNFA@QFP80 [DX3018]
R5F2L388BNFA@QFP80(single wire) [DX3018]
R5F2L388BNFP@QFP80 [DX3016]
R5F2L388BNFP@QFP80(single wire) [DX3016]
R5F2L388CDFA@QFP80 [DX3018]
R5F2L388CDFA@QFP80(single wire) [DX3018]
R5F2L388CDFP@QFP80 [DX3016]
R5F2L388CDFP@QFP80(single wire) [DX3016]
R5F2L388CNFA@QFP80 [DX3018]
R5F2L388CNFA@QFP80(single wire) [DX3018]
R5F2L388CNFP@QFP80 [DX3016]
R5F2L388CNFP@QFP80(single wire) [DX3016]
R5F2L38AADFA@QFP80 [DX3018]
R5F2L38AADFA@QFP80(single wire) [DX3018]
R5F2L38AADFP@QFP80 [DX3016]
R5F2L38AADFP@QFP80(single wire) [DX3016]
R5F2L38AANFA@QFP80 [DX3018]
R5F2L38AANFA@QFP80(single wire) [DX3018]
R5F2L38AANFP@QFP80 [DX3016]
R5F2L38AANFP@QFP80(single wire) [DX3016]
R5F2L38ABDFA@QFP80 [DX3018]
R5F2L38ABDFA@QFP80(single wire) [DX3018]
R5F2L38ABDFP@QFP80 [DX3016]
R5F2L38ABDFP@QFP80(single wire) [DX3016]
R5F2L38ABNFA@QFP80 [DX3018]
R5F2L38ABNFA@QFP80(single wire) [DX3018]
R5F2L38ABNFP@QFP80 [DX3016]
R5F2L38ABNFP@QFP80(single wire) [DX3016]
R5F2L38ACDFA@QFP80 [DX3018]
R5F2L38ACDFA@QFP80(single wire) [DX3018]
R5F2L38ACDFP@QFP80 [DX3016]

R5F2L38ACDFP@QFP80(single wire) [DX3016]
R5F2L38ACNFA@QFP80 [DX3018]
R5F2L38ACNFA@QFP80(single wire) [DX3018]
R5F2L38ACNFP@QFP80 [DX3016]
R5F2L38ACNFP@QFP80(single wire) [DX3016]
R5F2L38CADFA@QFP80 [DX3018]
R5F2L38CADFA@QFP80(single wire) [DX3018]
R5F2L38CADFP@QFP80 [DX3016]
R5F2L38CADFP@QFP80(single wire) [DX3016]
R5F2L38CANFA@QFP80 [DX3018]
R5F2L38CANFA@QFP80(single wire) [DX3018]
R5F2L38CANFP@QFP80 [DX3016]
R5F2L38CANFP@QFP80(single wire) [DX3016]
R5F2L38CBDFA@QFP80 [DX3018]
R5F2L38CBDFA@QFP80(single wire) [DX3018]
R5F2L38CBDFP@QFP80 [DX3016]
R5F2L38CBDFP@QFP80(single wire) [DX3016]
R5F2L38CBNFA@QFP80 [DX3018]
R5F2L38CBNFA@QFP80(single wire) [DX3018]
R5F2L38CBNFP@QFP80 [DX3016]
R5F2L38CBNFP@QFP80(single wire) [DX3016]
R5F2L38CCDFA@QFP80 [DX3018]
R5F2L38CCDFA@QFP80(single wire) [DX3018]
R5F2L38CCDFP@QFP80 [DX3016]
R5F2L38CCDFP@QFP80(single wire) [DX3016]
R5F2L38CCNFA@QFP80 [DX3018]
R5F2L38CCNFA@QFP80(single wire) [DX3018]
R5F2L38CCNFP@QFP80 [DX3016]
R5F2L38CCNFP@QFP80(single wire) [DX3016]
R5F2L3A7ADFA@PQFP100 [DX3023]
R5F2L3A7ADFA@PQFP100(single) [DX3023]
R5F2L3A7ADFP@PQFP100 [DX3021]
R5F2L3A7ADFP@PQFP100(single) [DX3021]
R5F2L3A7ANFA@PQFP100 [DX3023]
R5F2L3A7ANFA@PQFP100(single) [DX3023]
R5F2L3A7ANFP@PQFP100 [DX3021]
R5F2L3A7ANFP@PQFP100(single) [DX3021]
R5F2L3A7BDFA@PQFP100 [DX3023]
R5F2L3A7BDFA@PQFP100(single) [DX3023]
R5F2L3A7BDFP@PQFP100 [DX3021]
R5F2L3A7BDFP@PQFP100(single) [DX3021]
R5F2L3A7BNFA@PQFP100 [DX3023]
R5F2L3A7BNFA@PQFP100(single) [DX3023]
R5F2L3A7BNFP@PQFP100 [DX3021]
R5F2L3A7BNFP@PQFP100(single) [DX3021]
R5F2L3A7CDFA@PQFP100 [DX3023]
R5F2L3A7CDFA@PQFP100(single) [DX3023]
R5F2L3A7CDFP@PQFP100 [DX3021]

R5F2L3A7CDFP@PQFP100(single) [DX3021]
R5F2L3A7CNFA@PQFP100 [DX3023]
R5F2L3A7CNFA@PQFP100(single) [DX3023]
R5F2L3A7CNFP@PQFP100 [DX3021]
R5F2L3A7CNFP@PQFP100(single) [DX3021]
R5F2L3A8ADFA@PQFP100 [DX3023]
R5F2L3A8ADFA@PQFP100(single) [DX3023]
R5F2L3A8ADFP@PQFP100 [DX3021]
R5F2L3A8ADFP@PQFP100(single) [DX3021]
R5F2L3A8ANFA@PQFP100 [DX3023]
R5F2L3A8ANFA@PQFP100(single) [DX3023]
R5F2L3A8ANFP@PQFP100 [DX3021]
R5F2L3A8ANFP@PQFP100(single) [DX3021]
R5F2L3A8BDFA@PQFP100 [DX3023]
R5F2L3A8BDFA@PQFP100(single) [DX3023]
R5F2L3A8BDFP@PQFP100 [DX3021]
R5F2L3A8BDFP@PQFP100(single) [DX3021]
R5F2L3A8BNFA@PQFP100 [DX3023]
R5F2L3A8BNFA@PQFP100(single) [DX3023]
R5F2L3A8BNFP@PQFP100 [DX3021]
R5F2L3A8BNFP@PQFP100(single) [DX3021]
R5F2L3A8CDFA@PQFP100 [DX3023]
R5F2L3A8CDFA@PQFP100(single) [DX3023]
R5F2L3A8CDFP@PQFP100 [DX3021]
R5F2L3A8CDFP@PQFP100(single) [DX3021]
R5F2L3A8CNFA@PQFP100 [DX3023]
R5F2L3A8CNFA@PQFP100(single) [DX3023]
R5F2L3A8CNFP@PQFP100 [DX3021]
R5F2L3A8CNFP@PQFP100(single) [DX3021]
R5F2L3AAADFA@PQFP100 [DX3023]
R5F2L3AAADFA@PQFP100(single) [DX3023]
R5F2L3AAADFP@PQFP100 [DX3021]
R5F2L3AAADFP@PQFP100(single) [DX3021]
R5F2L3AAANFA@PQFP100 [DX3023]
R5F2L3AAANFA@PQFP100(single) [DX3023]
R5F2L3AAANFP@PQFP100 [DX3021]
R5F2L3AAANFP@PQFP100(single) [DX3021]
R5F2L3AABDFA@PQFP100 [DX3023]
R5F2L3AABDFA@PQFP100(single) [DX3023]
R5F2L3AABDFP@PQFP100 [DX3021]
R5F2L3AABDFP@PQFP100(single) [DX3021]
R5F2L3AABNFA@PQFP100 [DX3023]
R5F2L3AABNFA@PQFP100(single) [DX3023]
R5F2L3AABNFP@PQFP100 [DX3021]
R5F2L3AABNFP@PQFP100(single) [DX3021]
R5F2L3AACDFA@PQFP100 [DX3023]
R5F2L3AACDFA@PQFP100(single) [DX3023]
R5F2L3AACDFP@PQFP100 [DX3021]

R5F2L3AACDFP@PQFP100(single) [DX3021]
R5F2L3AACNFA@PQFP100 [DX3023]
R5F2L3AACNFA@PQFP100(single) [DX3023]
R5F2L3AACNFP@PQFP100 [DX3021]
R5F2L3AACNFP@PQFP100(single) [DX3021]
R5F2L3ACADFA@PQFP100 [DX3023]
R5F2L3ACADFA@PQFP100(single) [DX3023]
R5F2L3ACADFP@PQFP100 [DX3021]
R5F2L3ACADFP@PQFP100(single) [DX3021]
R5F2L3ACANFA@PQFP100 [DX3023]
R5F2L3ACANFA@PQFP100(single) [DX3023]
R5F2L3ACANFP@PQFP100 [DX3021]
R5F2L3ACANFP@PQFP100(single) [DX3021]
R5F2L3ACBDFA@PQFP100 [DX3023]
R5F2L3ACBDFA@PQFP100(single) [DX3023]
R5F2L3ACBDFP@PQFP100 [DX3021]
R5F2L3ACBDFP@PQFP100(single) [DX3021]
R5F2L3ACBNFA@PQFP100 [DX3023]
R5F2L3ACBNFA@PQFP100(single) [DX3023]
R5F2L3ACBNFP@PQFP100 [DX3021]
R5F2L3ACBNFP@PQFP100(single) [DX3021]
R5F2L3ACCDFA@PQFP100 [DX3023]
R5F2L3ACCDFA@PQFP100(single) [DX3023]
R5F2L3ACCDFP@PQFP100 [DX3021]
R5F2L3ACCDFP@PQFP100(single) [DX3021]
R5F2L3ACCNFA@PQFP100 [DX3023]
R5F2L3ACCNFA@PQFP100(single) [DX3023]
R5F2L3ACCNFP@PQFP100 [DX3021]
R5F2L3ACCNFP@PQFP100(single) [DX3021]
R5F2M110ADDD(single) [DX0001]
R5F2M110ADSP@TSSOP14(single) [DX1000]
R5F2M110ANDD(single) [DX0001]
R5F2M110ANSP@TSSOP14(single) [DX1000]
R5F2M111ADDD(single) [DX0001]
R5F2M111ADSP@TSSOP14(single) [DX1000]
R5F2M111ANDD(single) [DX0001]
R5F2M111ANSP@TSSOP14(single) [DX1000]
R5F2M112ADDD(single) [DX0001]
R5F2M112ADSP@TSSOP14(single) [DX1000]
R5F2M112ANDD(single) [DX0001]
R5F2M112ANSP@TSSOP14(single) [DX1000]
R5F2M120ADDD(single) [DX0001]
R5F2M120ADSP@TSSOP20(single) [DX1000]
R5F2M120ANDD(single) [DX0001]
R5F2M120ANSP@TSSOP20(single) [DX1000]
R5F2M121ADDD(single) [DX0001]
R5F2M121ADSP@TSSOP20(single) [DX1000]
R5F2M121ANDD(single) [DX0001]

R5F2M121ANSP@TSSOP20(single) [DX1000]
R5F2M122ADDD(single) [DX0001]
R5F2M122ADSP@TSSOP20(single) [DX1000]
R5F2M122ANDD(single) [DX0001]
R5F2M122ANSP@TSSOP20(single) [DX1000]

R5F35623JFE [DX3016]	R5F35623KFE [DX3016]
R5F35626JFE [DX3016]	R5F35626KFE [DX3016]
R5F3562EJFE [DX3016]	R5F3562EKFE [DX3016]
R5F35630JFF [DX3011]	R5F35630KFF [DX3011]
R5F35633JFF [DX3011]	R5F35633KFF [DX3011]
R5F35636JFF [DX3011]	R5F35636KFF [DX3011]
R5F3563EJFF [DX3011]	R5F3563EKFF [DX3011]
R5F35L23JFE [DX3016]	R5F35L23KFE [DX3016]
R5F35L26JFE [DX3016]	R5F35L26KFE [DX3016]
R5F35L2EJFE [DX3016]	R5F35L2EKFE [DX3016]
R5F35L30JFF [DX3011]	R5F35L30KFF [DX3011]
R5F35L33JFF [DX3011]	R5F35L33KFF [DX3011]
R5F35L36JFF [DX3011]	R5F35L36KFF [DX3011]
R5F35L3EJFF [DX3011]	R5F35L3EKFF [DX3011]
R5F363A6DFA@PQFP100 [DX3045]	R5F363A6DFB@QFP100 [DX3021]
R5F363A6NFA@PQFP100 [DX3045]	R5F363A6NFB@QFP100 [DX3021]
R5F363AEDFA@PQFP100 [DX3045]	R5F363AEDFB@QFP100 [DX3021]
R5F363AENFA@PQFP100 [DX3045]	R5F363AENFB@QFP100 [DX3021]
R5F363AKDFA@PQFP100 [DX3045]	R5F363AKDFB@QFP100 [DX3021]
R5F363AKNFA@PQFP100 [DX3045]	R5F363AKNFB@QFP100 [DX3021]
R5F363AMDFA@PQFP100 [DX3045]	R5F363AMDFB@QFP100 [DX3021]
R5F363AMNFA@PQFP100 [DX3045]	R5F363AMNFB@QFP100 [DX3021]
R5F36406DFA@PQFP100 [DX3045]	R5F36406DFB@QFP100 [DX3021]
R5F36406NFA@PQFP100 [DX3045]	R5F36406NFB@QFP100 [DX3021]
R5F3640DDFA@PQFP100 [DX3045]	R5F3640DDFB@QFP100 [DX3021]
R5F3640DNFA@PQFP100 [DX3045]	R5F3640DNFB@QFP100 [DX3021]
R5F3640MDFA@PQFP100 [DX3045]	R5F3640MDFB@QFP100 [DX3021]
R5F3640MNFA@PQFP100 [DX3045]	R5F3640MNFB@QFP100 [DX3021]
R5F364A6DFA@PQFP100 [DX3045]	R5F364A6DFB@QFP100 [DX3021]
R5F364A6NFA@PQFP100 [DX3045]	R5F364A6NFB@QFP100 [DX3021]
R5F364AEDFA@PQFP100 [DX3045]	R5F364AEDFB@QFP100 [DX3021]
R5F364AENFA@PQFP100 [DX3045]	R5F364AENFB@QFP100 [DX3021]
R5F364AMDFA@PQFP100 [DX3045]	R5F364AMDFB@QFP100 [DX3021]
R5F364AMNFA@PQFP100 [DX3045]	R5F364AMNFB@QFP100 [DX3021]
R5F36506DFA@PQFP100 [DX3045]	R5F36506DFB@QFP100 [DX3021]
R5F36506NFA@PQFP100 [DX3045]	R5F36506NFB@QFP100 [DX3021]
R5F3650EDFA@PQFP100 [DX3045]	R5F3650EDFB@QFP100 [DX3021]
R5F3650ENFA@PQFP100 [DX3045]	R5F3650ENFB@QFP100 [DX3021]
R5F3650KDFA@PQFP100 [DX3045]	R5F3650KDFB@QFP100 [DX3021]
R5F3650KNFA@PQFP100 [DX3045]	R5F3650KNFB@QFP100 [DX3021]
R5F3650MDFA@PQFP100 [DX3045]	R5F3650MDFB@QFP100 [DX3021]
R5F3650MNFA@PQFP100 [DX3045]	R5F3650MNFB@QFP100 [DX3021]
R5F3650NDFA@PQFP100 [DX3045]	R5F3650NDFB@QFP100 [DX3021]

R5F3650NNFA@PQFP100 [DX3045]	R5F3650NNFB@QFP100 [DX3021]
R5F3650RDFA@PQFP100 [DX3045]	R5F3650RDFB@QFP100 [DX3021]
R5F3650RNFA@PQFP100 [DX3045]	R5F3650RNFB@QFP100 [DX3021]
R5F3650TDFA@PQFP100 [DX3045]	R5F3650TDFB@QFP100 [DX3021]
R5F3650TNFA@PQFP100 [DX3045]	R5F3650TNFB@QFP100 [DX3021]
R5F3651EDFC@PQFP128 [DX3032]	R5F3651ENFC@PQFP128 [DX3032]
R5F3651KDFC@PQFP128 [DX3032]	R5F3651KNFC@PQFP128 [DX3032]
R5F3651MDFC@PQFP128 [DX3032]	R5F3651MNFC@PQFP128 [DX3032]
R5F3651NDFC@PQFP128 [DX3032]	R5F3651NNFC@PQFP128 [DX3032]
R5F3651RDFC@PQFP128 [DX3032]	R5F3651RNFC@PQFP128 [DX3032]
R5F3651TDFC@PQFP128 [DX3032]	R5F3651TNFC@PQFP128 [DX3032]
R5F36CA6DFA [DX3045]	R5F36CA6DFB [DX3021]
R5F36CA6NFA [DX3045]	R5F36CA6NFB [DX3021]
R5F36CAEDFA [DX3045]	R5F36CAEDFB [DX3021]
R5F36CAENFA [DX3045]	R5F36CAENFB [DX3021]
R5F36CAKDFA [DX3045]	R5F36CAKDFB [DX3021]
R5F36CAKNFA [DX3045]	R5F36CAKNFB [DX3021]
R5F36CAMDFA [DX3045]	R5F36CAMDFB [DX3021]
R5F36CAMNFA [DX3045]	R5F36CAMNFB [DX3021]
R5F64110DFB@TQFP100 [DX3021]	R5F64110NFB@TQFP100 [DX3021]
R5F64111DFB@TQFP100 [DX3021]	R5F64111NFB@TQFP100 [DX3021]
R5F64112DFB@TQFP100 [DX3021]	R5F64112NFB@TQFP100 [DX3021]
R5F64114DFB@TQFP100 [DX3021]	R5F64114NFB@TQFP100 [DX3021]
R5F64115DFB@TQFP100 [DX3021]	R5F64115NFB@TQFP100 [DX3021]
R5F64116DFB@TQFP100 [DX3021]	R5F64116NFB@TQFP100 [DX3021]
R5F6416JADFD [DX3035]	R5F6416JANFD [DX3035]
R5F6416JAPFD [DX3035]	R5F6416KADFD [DX3035]
R5F6416KANFD [DX3035]	R5F6416KAPFD [DX3035]
R5F6416LADFD [DX3035]	R5F6416LANFD [DX3035]
R5F6416LAPFD [DX3035]	R5F6416MADFD [DX3035]
R5F6416MANFD [DX3035]	R5F6416MAPFD [DX3035]
R5F64175DFB [DX3021]	R5F64175DFD [DX3035]
R5F64175NFB [DX3021]	R5F64175NFD [DX3035]
R5F64175PFB [DX3021]	R5F64175PFD [DX3035]
R5F64176DFB [DX3021]	R5F64176DFD [DX3035]
R5F64176NFB [DX3021]	R5F64176NFD [DX3035]
R5F64176PFB [DX3021]	R5F64176PFD [DX3035]
R5F64177DFB [DX3021]	R5F64177DFD [DX3035]
R5F64177NFB [DX3021]	R5F64177NFD [DX3035]
R5F64177PFB [DX3021]	R5F64177PFD [DX3035]
R5F64178DFB [DX3021]	R5F64178DFD [DX3035]
R5F64178NFB [DX3021]	R5F64178NFD [DX3035]
R5F64178PFB [DX3021]	R5F64178PFD [DX3035]
R5F64179DFB [DX3021]	R5F64179DFD [DX3035]
R5F64179NFB [DX3021]	R5F64179NFD [DX3035]
R5F64179PFB [DX3021]	R5F64179PFD [DX3035]
R5F64185DFB [DX3021]	R5F64185DFD [DX3035]
R5F64185HDFB [DX3021]	R5F64185HDFD [DX3035]

R5F64185HNFB [DX3021]
R5F64185HPFB [DX3021]
R5F64185NFB [DX3021]
R5F64185PFB [DX3021]
R5F64186DFB [DX3021]
R5F64186HDFB [DX3021]
R5F64186HNFB [DX3021]
R5F64186HPFB [DX3021]
R5F64186NFB [DX3021]
R5F64186PFB [DX3021]
R5F64187DFB [DX3021]
R5F64187HDFB [DX3021]
R5F64187HNFB [DX3021]
R5F64187HPFB [DX3021]
R5F64187NFB [DX3021]
R5F64187PFB [DX3021]
R5F64188DFB [DX3021]
R5F64188HDFB [DX3021]
R5F64188HNFB [DX3021]
R5F64188HPFB [DX3021]
R5F64188NFB [DX3021]
R5F64188PFB [DX3021]
R5F64189DFB [DX3021]
R5F64189HDFB [DX3021]
R5F64189HNFB [DX3021]
R5F64189HPFB [DX3021]
R5F64189NFB [DX3021]
R5F64189PFB [DX3021]
R5F64600JFP@QFP80 [DX3016]
R5F64600LFP@QFP80 [DX3016]
R5F64601KFP@QFP80 [DX3016]
R5F6460EJFP@QFP80 [DX3016]
R5F6460ELFP@QFP80 [DX3016]
R5F6460FKFP@QFP80 [DX3016]
R5F64610JFP@QFP80 [DX3016]
R5F64610LFP@QFP80 [DX3016]
R5F64611KFP@QFP80 [DX3016]
R5F6461EJFP@QFP80 [DX3016]
R5F6461ELFP@QFP80 [DX3016]
R5F6461FKFP@QFP80 [DX3016]
R5F646Z0JFP@QFP80 [DX3016]
R5F646Z0LFP@QFP80 [DX3016]
R5F646Z1KFP@QFP80 [DX3016]
R5F646ZEJFP@QFP80 [DX3016]
R5F646ZELFP@QFP80 [DX3016]
R5F646ZFKFP@QFP80 [DX3016]
R5G0C314D@SDIP32 [DX0032]
R5G0C514FA [DX3013]
R5F64185HNFD [DX3035]
R5F64185HPFD [DX3035]
R5F64185NFD [DX3035]
R5F64185PFD [DX3035]
R5F64186DFD [DX3035]
R5F64186HDFD [DX3035]
R5F64186HNFD [DX3035]
R5F64186HPFD [DX3035]
R5F64186NFD [DX3035]
R5F64186PFD [DX3035]
R5F64187DFD [DX3035]
R5F64187HDFD [DX3035]
R5F64187HNFD [DX3035]
R5F64187HPFD [DX3035]
R5F64187NFD [DX3035]
R5F64187PFD [DX3035]
R5F64188DFD [DX3035]
R5F64188HDFD [DX3035]
R5F64188HNFD [DX3035]
R5F64188HPFD [DX3035]
R5F64188NFD [DX3035]
R5F64188PFD [DX3035]
R5F64189DFD [DX3035]
R5F64189HDFD [DX3035]
R5F64189HNFD [DX3035]
R5F64189HPFD [DX3035]
R5F64189NFD [DX3035]
R5F64189PFD [DX3035]
R5F64600KFP@QFP80 [DX3016]
R5F64601JFP@QFP80 [DX3016]
R5F64601LFP@QFP80 [DX3016]
R5F6460EKFP@QFP80 [DX3016]
R5F6460FJFP@QFP80 [DX3016]
R5F6460FLFP@QFP80 [DX3016]
R5F64610KFP@QFP80 [DX3016]
R5F64611JFP@QFP80 [DX3016]
R5F64611LFP@QFP80 [DX3016]
R5F6461EKFP@QFP80 [DX3016]
R5F6461FJFP@QFP80 [DX3016]
R5F6461FLFP@QFP80 [DX3016]
R5F646Z0KFP@QFP80 [DX3016]
R5F646Z1JFP@QFP80 [DX3016]
R5F646Z1LFP@QFP80 [DX3016]
R5F646ZEKFP@QFP80 [DX3016]
R5F646ZFJFP@QFP80 [DX3016]
R5F646ZFLFP@QFP80 [DX3016]
R5G0C328FA@QFP32 [DX3001]
R5G0C514FP@QFP80 [DX3020]

R5R0C028FA@QFP32 [DX3010]
R5R0C0B4SP@TSSOP24(single wire) [DX1012]

MOSEL-VITELIC

E(E)PROM/FRAM/NVRAM

V29C31004B [DX0001]
V29C31004B@PLCC32 [DX2032]
V29C31004B@TSOP32 [DX1002]
V29C31004T [DX0001]
V29C31004T@PLCC32 [DX2032]
V29C31004T@TSOP32 [DX1002]
V29C51000B [DX0001]
V29C51000B@PLCC32 [DX2032]
V29C51000B@TSOP32 [DX1002]
V29C51000T [DX0001]
V29C51000T@PLCC32 [DX2032]
V29C51000T@TSOP32 [DX1002]
V29C51001B [DX0001]
V29C51001B@PLCC32 [DX2032]
V29C51001B@TSOP32 [DX1002]
V29C51001T [DX0001]
V29C51001T@PLCC32 [DX2032]
V29C51001T@TSOP32 [DX1002]
V29C51002B [DX0001]
V29C51002B@PLCC32 [DX2032]
V29C51002B@TSOP32 [DX1002]
V29C51002T [DX0001]
V29C51002T@PLCC32 [DX2032]
V29C51002T@TSOP32 [DX1002]
V29C51004B [DX0001]
V29C51004B@PLCC32 [DX2032]
V29C51004B@TSOP32 [DX1002]
V29C51004T [DX0001]
V29C51004T@PLCC32 [DX2032]
V29C51004T@TSOP32 [DX1002]
V29LC51000 [DX0001]
V29LC51000@PLCC32 [DX2032]
V29LC51000@TSOP32 [DX1002]
V29LC51001 [DX0001]
V29LC51001@PLCC32 [DX2032]
V29LC51001@TSOP32 [DX1002]
V29LC51002 [DX0001]
V29LC51002@PLCC32 [DX2032]
V29LC51002@TSOP32 [DX1002]

MICROCONTROLLER

MSU1958 [DX0001]
MSU1958@PLCC44 [DX2044]
MSU1958@TQFP44 [DX3002]
MSU2952 [DX0001]
MSU2952@PLCC44 [DX2044]
MSU2952@TQFP44 [DX3002]
MSU2958 [DX0001]
MSU2958@PLCC44 [DX2044]
MSU2958@TQFP44 [DX3002]
MSU2964 [DX0001]
MSU2964@PLCC44 [DX2044]
MSU2964@TQFP44 [DX3002]

MOSMIC

MICROCONTROLLER

MOS33001 [DX0001]
MOS33001@PLCC44 [DX2044]
MOS33001@TQFP44 [DX3005]
MOS33002 [DX0001]
MOS33002@PLCC44 [DX2044]
MOS33002@TQFP44 [DX3005]
MOS33004 [DX0001]
MOS33004@PLCC44 [DX2044]
MOS33004@TQFP44 [DX3005]
MOS33008 [DX0001]

MOS33008@PLCC44 [DX2044]
MOS33008@TQFP44 [DX3005]
MOS33016 [DX0001]
MOS33016@PLCC44 [DX2044]
MOS33016@TQFP44 [DX3005]
MOS33032 [DX0001]
MOS33032@PLCC44 [DX2044]
MOS33032@TQFP44 [DX3005]
MOS33064 [DX0001]
MOS33064@PLCC44 [DX2044]
MOS33064@TQFP44 [DX3005]
MOS33128 [DX0001]
MOS33128@PLCC44 [DX2044]
MOS33128@TQFP44 [DX3005]
MOS33256 [DX0001]
MOS33256@PLCC44 [DX2044]
MOS33256@TQFP44 [DX3005]

MOSTEK

E(E)PROM/FRAM/NVRAM

ET2716 [DX0001]
ETC2716 [DX0001]
ETC2732 [DX0001]
MK2716 [DX0001]
MK2764 [DX0001]
MK48C02 [DX0001]
MK48C12 [DX0001]
MK48T02 [DX0001]
MK48T08 [DX0001]
MK48T12 [DX0001]
MK48T12B [DX0001]
MK48T18 [DX0001]
MK48Z02 [DX0001]
MK48Z08 [DX0001]
MK48Z12 [DX0001]
MK48Z12B [DX0001]
MK48Z18 [DX0001]

MOTOROLA

E(E)PROM/FRAM/NVRAM

MC68764 [DX0001]
MC68766 [DX0001]
MCM2716 [DX0001]

DRAM & SRAM

MCM60256A [DX0001]
MCM60256A@SOIC28 [DX1035]
MCM60256AC [DX0001]
MCM60256AC@SOIC28 [DX1035]
MCM60256AV [DX0001]
MCM60256AV@SOIC28 [DX1035]
MCM60L256A [DX0001]
MCM60L256A@SOIC28 [DX1035]
MCM60L256AC [DX0001]
MCM60L256AC@SOIC28 [DX1035]
MCM60L256AV [DX0001]
MCM60L256AV@SOIC28 [DX1035]
MCM6206 [DX0001]
MCM6206@SOIC28 [DX1035]
MCM6206C [DX0001]
MCM6206C@SOIC28 [DX1035]
MCM6264 [DX0001]
MCM6264@SOIC28 [DX1035]
MCM6264C [DX0001]
MCM6264C@SOIC28 [DX1035]
MCM6706 [DX0001]
MCM6706@SOIC28 [DX1035]
MCM6706A [DX0001]
MCM6706A@SOJ28 [DX1035]

MICROCONTROLLER

DSP56F801(FA60)@TQFP48 [DX3007]
DSP56F801(FA60E)@TQFP48 [DX3007]
DSP56F801(FA80)@TQFP48 [DX3007]
DSP56F801(FA80E)@TQFP48 [DX3007]
DSP56F802(TA60)@TQFP32 [DX3001]
DSP56F802(TA60E)@TQFP32 [DX3001]
DSP56F802(TA80)@TQFP32 [DX3001]
DSP56F802(TA80E)@TQFP32 [DX3001]
DSP56F803(BU80)@TQFP100 [DX3021]
DSP56F803(BU80E)@TQFP100 [DX3021]
DSP56F805(FV80)@TQFP144 [DX3035]
DSP56F805(FV80E)@TQFP144 [DX3035]
DSP56F807(PY80)@LQFP160 [DX3090]
DSP56F807(PY80)@LQFP160(ISP)
DSP56F807(PY80E)@LQFP160 [DX3090]
DSP56F807(PY80E)@LQFP160(ISP)
DSP56F807(VF80)@LQFP160(ISP)
DSP56F807(VF80E)@LQFP160(ISP)
DSP56F826(BU80)@TQFP100 [DX3021]
DSP56F826(BU80)@TQFP100(ISP)
DSP56F826(BU80E)@TQFP100 [DX3021]
DSP56F826(BU80E)@TQFP100(ISP)
DSP56F827(FG80)@TQFP128 [DX3032]
DSP56F827(FG80E)@TQFP128 [DX3032]
MC13211@QFN65 [DX4023]
MC13212@QFN65 [DX4023]
MC13213@QFN65 [DX4023]
MC13214@QFN65 [DX4023]
MC56F8002VWL@SOIC28 [DX1033]
MC56F8006VLC@QFP32 [DX3001]
MC56F8006VLF@QFP48 [DX3007]
MC56F8006VWL@SOIC28 [DX1033]
MC56F8011VFAE@QFP32 [DX3001]
MC56F8013VFAE@QFP32 [DX3001]
MC56F8014VFAE@QFP32 [DX3001]
MC56F8023MFAE@QFP32 [DX3001]
MC56F8023VFAE@QFP32 [DX3001]
MC56F8025VLD@QFP44 [DX3003]
MC56F8027VLD@QFP64 [DX3011]
MC56F8033VLC@QFP32 [DX3001]
MC56F8035VLD@QFP44 [DX3003]
MC56F8036MFAE@QFP48 [DX3007]
MC56F8036VFAE@QFP48 [DX3007]
MC56F8037VLH@QFP64 [DX3011]
MC56F8122MFA@QFP48 [DX3007]
MC56F8122MFAE@QFP48 [DX3007]
MC56F8122VFA@QFP48 [DX3007]
MC56F8122VFAE@QFP48 [DX3007]
MC56F8123MFB@QFP64 [DX3011]
MC56F8123MFBE@QFP64 [DX3011]
MC56F8123VFB@QFP64 [DX3011]
MC56F8123VFBE@QFP64 [DX3011]
MC56F8135MFG@PQFP128 [DX3032]
MC56F8135MFGE@PQFP128 [DX3032]
MC56F8135VFG@PQFP128 [DX3032]
MC56F8135VFGE@PQFP128 [DX3032]
MC56F8145MFG@PQFP128 [DX3032]
MC56F8145MFGE@PQFP128 [DX3032]
MC56F8145VFG@PQFP128 [DX3032]
MC56F8145VFGE@PQFP128 [DX3032]
MC56F8146MFV@QFP144 [DX3035]
MC56F8146MFVE@QFP144 [DX3035]
MC56F8146VFV@QFP144 [DX3035]
MC56F8146VFVE@QFP144 [DX3035]
MC56F8147MPY@QFP160 [TA083A-B084]
MC56F8147MPYE@QFP160 [TA083A-B084]
MC56F8147VPY@QFP160 [TA083A-B084]
MC56F8147VPYE@QFP160 [TA083A-B084]
MC56F8155MFG@PQFP128 [DX3032]
MC56F8155MFGE@PQFP128 [DX3032]
MC56F8155VFG@PQFP128 [DX3032]
MC56F8155VFGE@PQFP128 [DX3032]
MC56F8156MFV@QFP144 [DX3035]
MC56F8156MFVE@QFP144 [DX3035]
MC56F8156VFV@QFP144 [DX3035]
MC56F8156VFVE@QFP144 [DX3035]
MC56F8157MPY@QFP160 [TA083A-B084]

MC56F8157MPYE@QFP160 [TA083A-B084]
MC56F8157VPY@QFP160 [TA083A-B084]
MC56F8157VPYE@QFP160 [TA083A-B084]
MC56F8165MFG@PQFP128 [DX3032]
MC56F8165MFGE@PQFP128 [DX3032]
MC56F8165VFG@PQFP128 [DX3032]
MC56F8165VFGE@PQFP128 [DX3032]
MC56F8166MFV@QFP144 [DX3035]
MC56F8166MFVE@QFP144 [DX3035]
MC56F8166VFV@QFP144 [DX3035]
MC56F8166VFVE@QFP144 [DX3035]
MC56F8167MPY@QFP160 [TA083A-B084]
MC56F8167MPYE@QFP160 [TA083A-B084]
MC56F8167VPY@QFP160 [TA083A-B084]
MC56F8167VPYE@QFP160 [TA083A-B084]
MC56F8246MLF@QFP48 [DX3007]
MC56F8246VLF@QFP48 [DX3007]
MC56F8247MLH@QFP64 [DX3011]
MC56F8247VLH@QFP64 [DX3011]
MC56F8256MLF@QFP48 [DX3007]
MC56F8256VLF@QFP48 [DX3007]
MC56F8257MLH@QFP64 [DX3011]
MC56F8257VLH@QFP64 [DX3011]
MC56F8322MFA@QFP48 [DX3007]
MC56F8322MFAE@QFP48 [DX3007]
MC56F8322VFA@QFP48 [DX3007]
MC56F8322VFAE@QFP48 [DX3007]
MC56F8323MFB@QFP64 [DX3011]
MC56F8323MFBE@QFP64 [DX3011]
MC56F8323VFB@QFP64 [DX3011]
MC56F8323VFBE@QFP64 [DX3011]
MC56F8335MFG@PQFP128 [DX3032]
MC56F8335MFGE@PQFP128 [DX3032]
MC56F8335VFG@PQFP128 [DX3032]
MC56F8335VFGE@PQFP128 [DX3032]
MC56F8345MFG@PQFP128 [DX3032]
MC56F8345MFGE@PQFP128 [DX3032]
MC56F8345VFG@PQFP128 [DX3032]
MC56F8345VFGE@PQFP128 [DX3032]
MC56F8346MFV@QFP144 [DX3035]
MC56F8346MFVE@QFP144 [DX3035]
MC56F8346VFV@QFP144 [DX3035]
MC56F8346VFVE@QFP144 [DX3035]
MC56F8347MPY@QFP160 [TA083A-B084]
MC56F8347MPYE@QFP160 [TA083A-B084]
MC56F8347VPY@QFP160 [TA083A-B084]
MC56F8347VPYE@QFP160 [TA083A-B084]
MC56F8355MFG@PQFP128 [DX3032]
MC56F8355MFGE@PQFP128 [DX3032]
MC56F8355VFG@PQFP128 [DX3032]
MC56F8355VFGE@PQFP128 [DX3032]
MC56F8356MFV@QFP144 [DX3035]
MC56F8356MFVE@QFP144 [DX3035]
MC56F8356VFV@QFP144 [DX3035]
MC56F8356VFVE@QFP144 [DX3035]
MC56F8357MPY@QFP160 [TA083A-B084]
MC56F8357MPYE@QFP160 [TA083A-B084]
MC56F8357VPY@QFP160 [TA083A-B084]
MC56F8357VPYE@QFP160 [TA083A-B084]
MC56F8365MFG@PQFP128 [DX3032]
MC56F8365MFGE@PQFP128 [DX3032]
MC56F8365VFG@PQFP128 [DX3032]
MC56F8365VFGE@PQFP128 [DX3032]
MC56F8366MFV@QFP144 [DX3035]
MC56F8366MFVE@QFP144 [DX3035]
MC56F8366VFV@QFP144 [DX3035]
MC56F8366VFVE@QFP144 [DX3035]
MC56F8367MPY@QFP160 [TA083A-B084]
MC56F8367MPYE@QFP160 [TA083A-B084]
MC56F8367VPY@QFP160 [TA083A-B084]
MC56F8367VPYE@QFP160 [TA083A-B084]
MC68HC11A0 [DX0001]
MC68HC11A0@PLCC52 [DX2052]
MC68HC11A1 [DX0001]
MC68HC11A1@PLCC52 [DX2052]
MC68HC11A8 [DX0001]
MC68HC11A8@PLCC52 [DX2052]

MC68HC11E1@PLCC52 [DX2052]
MC68HC11E1@QFP52 [DX3010]
MC68HC11E1CFU2 [DX3044]
MC68HC11E1CFU3 [DX3044]
MC68HC11E1MFU2 [DX3044]
MC68HC11E1VFU2 [DX3044]
MC68HC11E20@PLCC52 [DX2052]
MC68HC11E20@QFP52 [DX3010]
MC68HC11E20CFU2 [DX3044]
MC68HC11E20CFU3 [DX3044]
MC68HC11E20MFU2 [DX3044]
MC68HC11E20VFU2 [DX3044]
MC68HC11E9@PLCC52 [DX2052]
MC68HC11E9@QFP52 [DX3010]
MC68HC11E9CFU2 [DX3044]
MC68HC11E9CFU3 [DX3044]
MC68HC11E9MFU2 [DX3044]
MC68HC11E9VFU2 [DX3044]
MC68HC11EA9CFN2 [DX2052]
MC68HC11EA9CFN3 [DX2052]
MC68HC11EA9CFS2 [DX2052]
MC68HC11EA9CFS3 [DX2052]
MC68HC11EA9MFN2 [DX2052]
MC68HC11EA9MFN3 [DX2052]
MC68HC11EA9MFS2 [DX2052]
MC68HC11EA9MFS3 [DX2052]
MC68HC11EA9VFN2 [DX2052]
MC68HC11EA9VFN3 [DX2052]
MC68HC11EA9VFS2 [DX2052]
MC68HC11EA9VFS3 [DX2052]
MC68HC11F1@PLCC68 [DX2068]
MC68HC11F1A@PLCC68 [DX2068]
MC68HC11F1ACFN2 [DX2068]
MC68HC11F1ACFN3 [DX2068]
MC68HC11F1ACFN4 [DX2068]
MC68HC11F1ACPU2 [DX3017]
MC68HC11F1ACPU3 [DX3017]
MC68HC11F1ACPU4 [DX3017]
MC68HC11F1AMFN2 [DX2068]
MC68HC11F1AMFN3 [DX2068]
MC68HC11F1AMFN4 [DX2068]
MC68HC11F1AMPU2 [DX3017]
MC68HC11F1AMPU3 [DX3017]
MC68HC11F1AMPU4 [DX3017]
MC68HC11F1AVFN2 [DX2068]
MC68HC11F1AVFN3 [DX2068]
MC68HC11F1AVFN4 [DX2068]
MC68HC11F1AVPU2 [DX3017]
MC68HC11F1AVPU3 [DX3017]
MC68HC11F1AVPU4 [DX3017]
MC68HC11F1CFN2 [DX2068]
MC68HC11F1CFN3 [DX2068]
MC68HC11F1CFN4 [DX2068]
MC68HC11F1CPU2 [DX3017]
MC68HC11F1CPU3 [DX3017]
MC68HC11F1CPU4 [DX3017]
MC68HC11F1MFN2 [DX2068]
MC68HC11F1MFN3 [DX2068]
MC68HC11F1MFN4 [DX2068]
MC68HC11F1MPU2 [DX3017]
MC68HC11F1MPU3 [DX3017]
MC68HC11F1MPU4 [DX3017]
MC68HC11F1VFN2 [DX2068]
MC68HC11F1VFN3 [DX2068]
MC68HC11F1VFN4 [DX2068]
MC68HC11F1VPU2 [DX3017]
MC68HC11F1VPU3 [DX3017]
MC68HC11F1VPU4 [DX3017]
MC68HC11K1@PLCC84 [DX2084]
MC68HC11K1@TQFP80 [DX3018]
MC68HC11KS2@PLCC68 [DX2068]
MC68HC11P1CFN3 [DX2084]
MC68HC11P1CFN4 [DX2084]
MC68HC11P2CFN3 [DX2084]
MC68HC11P2CFN4 [DX2084]
MC68HC11P3CFN3 [DX2084]
MC68HC11P3CFN4 [DX2084]
MC68HC705B16B [DX0056]
MC68HC705B16CB [DX0056]
MC68HC705B16CFN [DX2052]
MC68HC705B16CFU [DX3013]
MC68HC705B16FN [DX2052]
MC68HC705B16FU [DX3013]
MC68HC705B16NB [DX0056]
MC68HC705B16NCB [DX0056]
MC68HC705B16NCFN [DX2052]
MC68HC705B16NCFU [DX3013]
MC68HC705B16NFN [DX2052]
MC68HC705B16NFU [DX3013]
MC68HC705C4 [DX0001]
MC68HC705C4@PLCC44 [DX2044]
MC68HC705C4A [DX0001]
MC68HC705C4A@PLCC44 [DX2044]
MC68HC705C8 [DX0001]
MC68HC705C8@PLCC44 [DX2044]
MC68HC705C8@SDIP42 [DX0042]

MC68HC705C8@TQFP44 [DX3002]
MC68HC705C8A [DX0001]
MC68HC705C8A@PLCC44 [DX2044]
MC68HC705C8A@SDIP42 [DX0042]
MC68HC705C8A@TQFP44 [DX3002]
MC68HC705C9A [DX0001]
MC68HC705C9A@PLCC44 [DX2044]
MC68HC705C9A@TQFP44 [DX3002]
MC68HC705J1ACDW [DX1033]
MC68HC705J1ACP [DX0001]
MC68HC705J1ACS [DX1001]
MC68HC705J1ADW [DX1033]
MC68HC705J1AP [DX0001]
MC68HC705J1AS [DX1001]
MC68HC705KJ1CDW [DX1033]
MC68HC705KJ1CP [DX0001]
MC68HC705KJ1CS [DX1001]
MC68HC705KJ1DW [DX1033]
MC68HC705KJ1P [DX0001]
MC68HC705KJ1S [DX1001]
MC68HC705P6(CDW)@SOIC28 [DX1033]
MC68HC705P6(CP) [DX0001]
MC68HC705P6A(CDW)@SOIC28 [DX1033]
MC68HC705P6A(CP) [DX0001]
MC68HC705P9 [DX0001]
MC68HC705P9@SOIC28 [DX1033]
MC68HC705SR3 [DX0001]
MC68HC705SR3@SDIP42 [DX0042]
MC68HC705SR3@TQFP44 [DX3005]
MC68HC711D3 [DX0001]
MC68HC711D3(3V) [DX0001]
MC68HC711D3(3V)@PLCC44 [DX2044]
MC68HC711D3(3V)@TQFP44 [DX3002]
MC68HC711D3@PLCC44 [DX2044]
MC68HC711D3@TQFP44 [DX3002]
MC68HC711E20@PLCC52 [DX2052]
MC68HC711E9@PLCC52 [DX2052]
MC68HC711E9CFN@PLCC52 [DX2052]
MC68HC711E9CFN2@PLCC52 [DX2052]
MC68HC711E9CFN3@PLCC52 [DX2052]
MC68HC711E9CFNE@PLCC52 [DX2052]
MC68HC711E9CFNE2@PLCC52 [DX2052]
MC68HC711E9CFNE3@PLCC52 [DX2052]
MC68HC711E9FN@PLCC52 [DX2052]
MC68HC711E9MFN2@PLCC52 [DX2052]
MC68HC711E9MFNE2@PLCC52 [DX2052]
MC68HC711E9VFN2@PLCC52 [DX2052]
MC68HC711E9VFNE2@PLCC52 [DX2052]
MC68HC711EA9CFN2 [DX2052]
MC68HC711EA9CFN3 [DX2052]
MC68HC711EA9CFS2 [DX2052]
MC68HC711EA9CFS3 [DX2052]
MC68HC711EA9MFN2 [DX2052]
MC68HC711EA9MFN3 [DX2052]
MC68HC711EA9MFS2 [DX2052]
MC68HC711EA9MFS3 [DX2052]
MC68HC711EA9VFN2 [DX2052]
MC68HC711EA9VFN3 [DX2052]
MC68HC711EA9VFS2 [DX2052]
MC68HC711EA9VFS3 [DX2052]
MC68HC711K4@PLCC84 [DX2084]
MC68HC711K4@TQFP80 [DX3018]
MC68HC711KA2@PLCC68 [DX2068]
MC68HC711KA3@PLCC68 [DX2068]
MC68HC711KA4@PLCC68 [DX2068]
MC68HC711KS2@PLCC68 [DX2068]
MC68HC711L6@PLCC68 [DX2068]
MC68HC711L6@TQFP64 [DX3013]
MC68HC711P2CFN3 [DX2084]
MC68HC711P2CFN4 [DX2084]
MC68HC711P2CFS3 [DX2084]
MC68HC711P2CFS4 [DX2084]
MC68HC811E2 [DX0001]
MC68HC811E2@PLCC52 [DX2052]
MC68HC811E2C [DX0001]
MC68HC811E2M [DX0001]
MC68HC811E2V [DX0001]
MC68HC812A4CPV@TQFP112 [DX3026]
MC68HC812A4CPVE@TQFP112 [DX3026]
MC68HC812A4MPV@TQFP112 [DX3026]
MC68HC812A4MPVE@TQFP112 [DX3026]
MC68HC812A4VPV@TQFP112 [DX3026]
MC68HC812A4VPVE@TQFP112 [DX3026]
MC68HC908AB32CFU@TQFP64 [DX3014]
MC68HC908AB32CFUE@TQFP64 [DX3014]
MC68HC908AB32MFU@TQFP64 [DX3014]
MC68HC908AB32MFUE@TQFP64 [DX3014]
MC68HC908AB32VFU@TQFP64 [DX3014]
MC68HC908AB32VFUE@TQFP64 [DX3014]

MC68HC908AP16CB@SDIP42 [DX0042]
MC68HC908AP16CBE@SDIP42 [DX0042]
MC68HC908AP16CFA@LQFP48 [DX3007]
MC68HC908AP16CFAE@LQFP48 [DX3007]
MC68HC908AP16CFB@TQFP44 [DX3002]
MC68HC908AP16CFBE@TQFP44 [DX3002]
MC68HC908AP16MB@SDIP42 [DX0042]
MC68HC908AP16MBE@SDIP42 [DX0042]
MC68HC908AP16MFA@LQFP48 [DX3007]
MC68HC908AP16MFAE@LQFP48 [DX3007]
MC68HC908AP16MFB@TQFP44 [DX3002]
MC68HC908AP16MFBE@TQFP44 [DX3002]
MC68HC908AP16VB@SDIP42 [DX0042]
MC68HC908AP16VBE@SDIP42 [DX0042]
MC68HC908AP16VFA@LQFP48 [DX3007]
MC68HC908AP16VFAE@LQFP48 [DX3007]
MC68HC908AP16VFB@TQFP44 [DX3002]
MC68HC908AP16VFBE@TQFP44 [DX3002]
MC68HC908AP32CB@SDIP42 [DX0042]
MC68HC908AP32CBE@SDIP42 [DX0042]
MC68HC908AP32CFA@LQFP48 [DX3007]
MC68HC908AP32CFAE@LQFP48 [DX3007]
MC68HC908AP32CFB@TQFP44 [DX3002]
MC68HC908AP32CFBE@TQFP44 [DX3002]
MC68HC908AP32MB@SDIP42 [DX0042]
MC68HC908AP32MBE@SDIP42 [DX0042]
MC68HC908AP32MFA@LQFP48 [DX3007]
MC68HC908AP32MFAE@LQFP48 [DX3007]
MC68HC908AP32MFB@TQFP44 [DX3002]
MC68HC908AP32MFBE@TQFP44 [DX3002]
MC68HC908AP32VB@SDIP42 [DX0042]
MC68HC908AP32VBE@SDIP42 [DX0042]
MC68HC908AP32VFA@LQFP48 [DX3007]
MC68HC908AP32VFAE@LQFP48 [DX3007]
MC68HC908AP32VFB@TQFP44 [DX3002]
MC68HC908AP32VFBE@TQFP44 [DX3002]
MC68HC908AP64CB@SDIP42 [DX0042]
MC68HC908AP64CBE@SDIP42 [DX0042]
MC68HC908AP64CFA@LQFP48 [DX3007]
MC68HC908AP64CFAE@LQFP48 [DX3007]
MC68HC908AP64CFB@TQFP44 [DX3002]
MC68HC908AP64CFBE@TQFP44 [DX3002]
MC68HC908AP64MB@SDIP42 [DX0042]
MC68HC908AP64MBE@SDIP42 [DX0042]
MC68HC908AP64MFA@LQFP48 [DX3007]
MC68HC908AP64MFAE@LQFP48 [DX3007]
MC68HC908AP64MFB@TQFP44 [DX3002]
MC68HC908AP64MFBE@TQFP44 [DX3002]
MC68HC908AP64VB@SDIP42 [DX0042]
MC68HC908AP64VBE@SDIP42 [DX0042]
MC68HC908AP64VFA@LQFP48 [DX3007]
MC68HC908AP64VFAE@LQFP48 [DX3007]
MC68HC908AP64VFB@TQFP44 [DX3002]
MC68HC908AP64VFBE@TQFP44 [DX3002]
MC68HC908AP8CB@SDIP42 [DX0042]
MC68HC908AP8CBE@SDIP42 [DX0042]
MC68HC908AP8CFA@LQFP48 [DX3007]
MC68HC908AP8CFAE@LQFP48 [DX3007]
MC68HC908AP8CFB@TQFP44 [DX3002]
MC68HC908AP8CFBE@TQFP44 [DX3002]

MC68HC908AP8MB@SDIP42 [DX0042]
MC68HC908AP8MBE@SDIP42 [DX0042]
MC68HC908AP8MFA@LQFP48 [DX3007]
MC68HC908AP8MFAE@LQFP48 [DX3007]
MC68HC908AP8MFB@TQFP44 [DX3002]
MC68HC908AP8MFBE@TQFP44 [DX3002]
MC68HC908AP8VB@SDIP42 [DX0042]
MC68HC908AP8VBE@SDIP42 [DX0042]
MC68HC908AP8VFA@LQFP48 [DX3007]
MC68HC908AP8VFAE@LQFP48 [DX3007]
MC68HC908AP8VFB@TQFP44 [DX3002]
MC68HC908AP8VFBE@TQFP44 [DX3002]
MC68HC908AS32ACFN@PLCC52 [DX2052]
MC68HC908AS32ACFNE@PLCC52 [DX2052]
MC68HC908AS32ACFU@TQFP64 [DX3014]
MC68HC908AS32ACFUE@TQFP64 [DX3014]
MC68HC908AS32AMFN@PLCC52 [DX2052]
MC68HC908AS32AMFNE@PLCC52 [DX2052]
MC68HC908AS32AMFU@TQFP64 [DX3014]
MC68HC908AS32AMFUE@TQFP64 [DX3014]
MC68HC908AS32AVFN@PLCC52 [DX2052]
MC68HC908AS32AVFNE@PLCC52 [DX2052]
MC68HC908AS32AVFU@TQFP64 [DX3014]
MC68HC908AS32AVFUE@TQFP64 [DX3014]
MC68HC908AS60ACFN@PLCC52 [DX2052]
MC68HC908AS60ACFU@TQFP64 [DX3014]
MC68HC908AS60AMFN@PLCC52 [DX2052]
MC68HC908AS60AMFU@TQFP64 [DX3014]
MC68HC908AS60AVFN@PLCC52 [DX2052]
MC68HC908AS60AVFU@TQFP64 [DX3014]
MC68HC908AS60CFN@PLCC52 [DX2052]
MC68HC908AS60CFU@TQFP64 [DX3014]
MC68HC908AS60MFN@PLCC52 [DX2052]
MC68HC908AS60MFU@TQFP64 [DX3014]
MC68HC908AS60VFN@PLCC52 [DX2052]
MC68HC908AS60VFU@TQFP64 [DX3014]
MC68HC908AZ32ACFU@TQFP64 [DX3014]
MC68HC908AZ32ACFUE@TQFP64 [DX3014]
MC68HC908AZ32AMFU@TQFP64 [DX3014]
MC68HC908AZ32AMFUE@TQFP64 [DX3014]
MC68HC908AZ32AVFU@TQFP64 [DX3014]
MC68HC908AZ32AVFUE@TQFP64 [DX3014]
MC68HC908AZ60ACFU@TQFP64 [DX3014]
MC68HC908AZ60ACFUE@TQFP64 [DX3014]
MC68HC908AZ60AMFU@TQFP64 [DX3014]
MC68HC908AZ60AMFUE@TQFP64 [DX3014]
MC68HC908AZ60AVFU@TQFP64 [DX3014]
MC68HC908AZ60AVFUE@TQFP64 [DX3014]
MC68HC908AZ60CFU@TQFP64 [DX3014]
MC68HC908AZ60MFU@TQFP64 [DX3014]
MC68HC908AZ60VFU@TQFP64 [DX3014]
MC68HC908BD48IB@SDIP42 [DX0042]
MC68HC908BD48IBE@SDIP42 [DX0042]
MC68HC908BD48IFB@TQFP44 [DX3002]
MC68HC908BD48IFBE@TQFP44 [DX3002]
MC68HC908EY16ACFJ@TQFP32 [DX3001]
MC68HC908EY16ACFJE@TQFP32 [DX3001]
MC68HC908EY16AKFJ@TQFP32 [DX3001]
MC68HC908EY16AKFJE@TQFP32 [DX3001]
MC68HC908EY16AMFJ@TQFP32 [DX3001]

MC68HC908EY16AMFJE@TQFP32 [DX3001]
MC68HC908EY16AVFJ@TQFP32 [DX3001]
MC68HC908EY16AVFJE@TQFP32 [DX3001]
MC68HC908EY16CFA@TQFP32 [DX3001]
MC68HC908EY16CFAE@TQFP32 [DX3001]
MC68HC908EY16KFA@TQFP32 [DX3001]
MC68HC908EY16KFAE@TQFP32 [DX3001]
MC68HC908EY16MFA@TQFP32 [DX3001]
MC68HC908EY16MFAE@TQFP32 [DX3001]
MC68HC908EY16VFA@TQFP32 [DX3001]
MC68HC908EY16VFAE@TQFP32 [DX3001]
MC68HC908EY8ACFJ@TQFP32 [DX3001]
MC68HC908EY8ACFJE@TQFP32 [DX3001]
MC68HC908EY8AKFJ@TQFP32 [DX3001]
MC68HC908EY8AKFJE@TQFP32 [DX3001]
MC68HC908EY8AMFJ@TQFP32 [DX3001]
MC68HC908EY8AMFJE@TQFP32 [DX3001]
MC68HC908EY8AVFJ@TQFP32 [DX3001]
MC68HC908EY8AVFJE@TQFP32 [DX3001]
MC68HC908EY8CFA@TQFP32 [DX3001]
MC68HC908EY8CFAE@TQFP32 [DX3001]
MC68HC908EY8KFA@TQFP32 [DX3001]
MC68HC908EY8KFAE@TQFP32 [DX3001]
MC68HC908EY8MFA@TQFP32 [DX3001]
MC68HC908EY8MFAE@TQFP32 [DX3001]
MC68HC908EY8VFA@TQFP32 [DX3001]
MC68HC908EY8VFAE@TQFP32 [DX3001]
MC68HC908GP32CB@SDIP42 [DX0042]
MC68HC908GP32CBE@SDIP42 [DX0042]
MC68HC908GP32CFB@TQFP44 [DX3002]
MC68HC908GP32CFBE@TQFP44 [DX3002]
MC68HC908GP32CP
MC68HC908GP32CPE
MC68HC908GP32MB@SDIP42 [DX0042]
MC68HC908GP32MBE@SDIP42 [DX0042]
MC68HC908GP32MFB@TQFP44 [DX3002]
MC68HC908GP32MFBE@TQFP44 [DX3002]
MC68HC908GP32MP
MC68HC908GP32MPE
MC68HC908GP32VB@SDIP42 [DX0042]
MC68HC908GP32VBE@SDIP42 [DX0042]
MC68HC908GP32VFB@TQFP44 [DX3002]
MC68HC908GP32VFBE@TQFP44 [DX3002]
MC68HC908GP32VP
MC68HC908GP32VPE
MC68HC908GR16ACFA@TQFP48 [DX3007]
MC68HC908GR16ACFAE@TQFP48 [DX3007]
MC68HC908GR16ACFJ@TQFP32 [DX3001]
MC68HC908GR16ACFJE@TQFP32 [DX3001]
MC68HC908GR16AMFA@TQFP48 [DX3007]
MC68HC908GR16AMFAE@TQFP48 [DX3007]
MC68HC908GR16AMFJ@TQFP32 [DX3001]
MC68HC908GR16AMFJE@TQFP32 [DX3001]
MC68HC908GR16AVFA@TQFP48 [DX3007]
MC68HC908GR16AVFAE@TQFP48 [DX3007]
MC68HC908GR16AVFJ@TQFP32 [DX3001]
MC68HC908GR16AVFJE@TQFP32 [DX3001]
MC68HC908GR16CFA@TQFP48 [DX3007]

MC68HC908GR16CFAE@TQFP48 [DX3007]
MC68HC908GR16CFJ@TQFP32 [DX3001]
MC68HC908GR16CFJE@TQFP32 [DX3001]
MC68HC908GR16MFA@TQFP48 [DX3007]
MC68HC908GR16MFAE@TQFP48 [DX3007]
MC68HC908GR16MFJ@TQFP32 [DX3001]
MC68HC908GR16MFJE@TQFP32 [DX3001]
MC68HC908GR16VFA@TQFP48 [DX3007]
MC68HC908GR16VFAE@TQFP48 [DX3007]
MC68HC908GR16VFJ@TQFP32 [DX3001]
MC68HC908GR16VFJE@TQFP32 [DX3001]
MC68HC908GR32ACFA@TQFP48 [DX3007]
MC68HC908GR32ACFAE@TQFP48 [DX3007]
MC68HC908GR32ACFJ@TQFP32 [DX3001]
MC68HC908GR32ACFJE@TQFP32 [DX3001]
MC68HC908GR32ACFU@QFP64 [DX3014]
MC68HC908GR32ACFUE@QFP64 [DX3014]
MC68HC908GR32AMFA@TQFP48 [DX3007]
MC68HC908GR32AMFAE@TQFP48 [DX3007]
MC68HC908GR32AMFJ@TQFP32 [DX3001]
MC68HC908GR32AMFJE@TQFP32 [DX3001]
MC68HC908GR32AMFU@QFP64 [DX3014]
MC68HC908GR32AMFUE@QFP64 [DX3014]
MC68HC908GR32AVFA@TQFP48 [DX3007]
MC68HC908GR32AVFAE@TQFP48 [DX3007]
MC68HC908GR32AVFJ@TQFP32 [DX3001]
MC68HC908GR32AVFJE@TQFP32 [DX3001]
MC68HC908GR32AVFU@QFP64 [DX3014]
MC68HC908GR32AVFUE@QFP64 [DX3014]
MC68HC908GR48ACFA@TQFP48 [DX3007]
MC68HC908GR48ACFAE@TQFP48 [DX3007]
MC68HC908GR48ACFJ@TQFP32 [DX3001]
MC68HC908GR48ACFJE@TQFP32 [DX3001]
MC68HC908GR48ACFU@QFP64 [DX3014]
MC68HC908GR48ACFUE@QFP64 [DX3014]
MC68HC908GR48AMFA@TQFP48 [DX3007]
MC68HC908GR48AMFAE@TQFP48 [DX3007]
MC68HC908GR48AMFJ@TQFP32 [DX3001]
MC68HC908GR48AMFJE@TQFP32 [DX3001]
MC68HC908GR48AMFU@QFP64 [DX3014]
MC68HC908GR48AMFUE@QFP64 [DX3014]
MC68HC908GR48AVFA@TQFP48 [DX3007]
MC68HC908GR48AVFAE@TQFP48 [DX3007]
MC68HC908GR48AVFJ@TQFP32 [DX3001]
MC68HC908GR48AVFJE@TQFP32 [DX3001]
MC68HC908GR48AVFU@QFP64 [DX3014]
MC68HC908GR48AVFUE@QFP64 [DX3014]
MC68HC908GR4ACDW@SOIC28 [DX1033]

MC68HC908GR4ACDWE@SOIC28 [DX1033]
MC68HC908GR4ACFA@TQFP32 [DX3001]
MC68HC908GR4ACFAE@TQFP32 [DX3001]
MC68HC908GR4ACP MC68HC908GR4ACPE
MC68HC908GR4AMDW@SOIC28 [DX1033]
MC68HC908GR4AMDWE@SOIC28 [DX1033]
MC68HC908GR4AMFA@TQFP32 [DX3001]
MC68HC908GR4AMFAE@TQFP32 [DX3001]
MC68HC908GR4AMP MC68HC908GR4AMPE
MC68HC908GR4AVDW@SOIC28 [DX1033]
MC68HC908GR4AVDWE@SOIC28 [DX1033]
MC68HC908GR4AVFA@TQFP32 [DX3001]
MC68HC908GR4AVFAE@TQFP32 [DX3001]
MC68HC908GR4AVP MC68HC908GR4AVPE
MC68HC908GR4CB@SDIP42 [DX0042] MC68HC908GR4CBE@SDIP42 [DX0042]
MC68HC908GR4CDW@SOIC28 [DX1033] MC68HC908GR4CDWE@SOIC28 [DX1033]
MC68HC908GR4CFA@TQFP32 [DX3001] MC68HC908GR4CFAE@TQFP32 [DX3001]
MC68HC908GR4CP MC68HC908GR4CPE
MC68HC908GR4MB@SDIP42 [DX0042] MC68HC908GR4MBE@SDIP42 [DX0042]
MC68HC908GR4MDW@SOIC28 [DX1033] MC68HC908GR4MDWE@SOIC28 [DX1033]
MC68HC908GR4MFA@TQFP32 [DX3001] MC68HC908GR4MFAE@TQFP32 [DX3001]
MC68HC908GR4MP MC68HC908GR4MPE
MC68HC908GR4VB@SDIP42 [DX0042] MC68HC908GR4VBE@SDIP42 [DX0042]
MC68HC908GR4VDW@SOIC28 [DX1033] MC68HC908GR4VDWE@SOIC28 [DX1033]
MC68HC908GR4VFA@TQFP32 [DX3001] MC68HC908GR4VFAE@TQFP32 [DX3001]
MC68HC908GR4VP MC68HC908GR4VPE
MC68HC908GR60ACFA@TQFP48 [DX3007]
MC68HC908GR60ACFAE@TQFP48 [DX3007]
MC68HC908GR60ACFJ@TQFP32 [DX3001]
MC68HC908GR60ACFJE@TQFP32 [DX3001]
MC68HC908GR60ACFU@QFP64 [DX3014]
MC68HC908GR60ACFUE@QFP64 [DX3014]
MC68HC908GR60AMFA@TQFP48 [DX3007]
MC68HC908GR60AMFAE@TQFP48 [DX3007]
MC68HC908GR60AMFJ@TQFP32 [DX3001]
MC68HC908GR60AMFJE@TQFP32 [DX3001]
MC68HC908GR60AMFU@QFP64 [DX3014]
MC68HC908GR60AMFUE@QFP64 [DX3014]
MC68HC908GR60AVFA@TQFP48 [DX3007]
MC68HC908GR60AVFAE@TQFP48 [DX3007]
MC68HC908GR60AVFJ@TQFP32 [DX3001]
MC68HC908GR60AVFJE@TQFP32 [DX3001]
MC68HC908GR60AVFU@QFP64 [DX3014]
MC68HC908GR60AVFUE@QFP64 [DX3014]
MC68HC908GR8ACDW@SOIC28 [DX1033]
MC68HC908GR8ACDWE@SOIC28 [DX1033]
MC68HC908GR8ACFA@TQFP32 [DX3001]
MC68HC908GR8ACFAE@TQFP32 [DX3001]

MC68HC908GR8ACP MC68HC908GR8ACPE
MC68HC908GR8AMDW@SOIC28 [DX1033]
MC68HC908GR8AMDWE@SOIC28 [DX1033]
MC68HC908GR8AMFA@TQFP32 [DX3001]
MC68HC908GR8AMFAE@TQFP32 [DX3001]
MC68HC908GR8AMP MC68HC908GR8AMPE
MC68HC908GR8AVDW@SOIC28 [DX1033]
MC68HC908GR8AVDWE@SOIC28 [DX1033]
MC68HC908GR8AVFA@TQFP32 [DX3001]
MC68HC908GR8AVFAE@TQFP32 [DX3001]
MC68HC908GR8AVP MC68HC908GR8AVPE
MC68HC908GR8CB@SDIP42 [DX0042] MC68HC908GR8CBE@SDIP42 [DX0042]
MC68HC908GR8CDW@SOIC28 [DX1033] MC68HC908GR8CDWE@SOIC28 [DX1033]
MC68HC908GR8CFA@TQFP32 [DX3001] MC68HC908GR8CFAE@TQFP32 [DX3001]
MC68HC908GR8CP MC68HC908GR8CPE
MC68HC908GR8MB@SDIP42 [DX0042] MC68HC908GR8MBE@SDIP42 [DX0042]
MC68HC908GR8MDW@SOIC28 [DX1033] MC68HC908GR8MDWE@SOIC28 [DX1033]
MC68HC908GR8MFA@TQFP32 [DX3001] MC68HC908GR8MFAE@TQFP32 [DX3001]
MC68HC908GR8MP MC68HC908GR8MPE
MC68HC908GR8VB@SDIP42 [DX0042] MC68HC908GR8VBE@SDIP42 [DX0042]
MC68HC908GR8VDW@SOIC28 [DX1033] MC68HC908GR8VDWE@SOIC28 [DX1033]
MC68HC908GR8VFA@TQFP32 [DX3001] MC68HC908GR8VFAE@TQFP32 [DX3001]
MC68HC908GR8VP MC68HC908GR8VPE
MC68HC908GT16CB@SDIP42 [DX0042] MC68HC908GT16CBE@SDIP42 [DX0042]
MC68HC908GT16CFB@TQFP44 [DX3002]
MC68HC908GT16CFBE@TQFP44 [DX3002]
MC68HC908GT16MB@SDIP42 [DX0042] MC68HC908GT16MBE@SDIP42 [DX0042]
MC68HC908GT16MFB@TQFP44 [DX3002]
MC68HC908GT16MFBE@TQFP44 [DX3002]
MC68HC908GT16VB@SDIP42 [DX0042] MC68HC908GT16VBE@SDIP42 [DX0042]
MC68HC908GT16VFB@TQFP44 [DX3002]
MC68HC908GT16VFBE@TQFP44 [DX3002]
MC68HC908GT8CB@SDIP42 [DX0042] MC68HC908GT8CBE@SDIP42 [DX0042]
MC68HC908GT8CFB@TQFP44 [DX3002] MC68HC908GT8CFBE@TQFP44 [DX3002]
MC68HC908GT8MB@SDIP42 [DX0042] MC68HC908GT8MBE@SDIP42 [DX0042]
MC68HC908GT8MFB@TQFP44 [DX3002] MC68HC908GT8MFBE@TQFP44 [DX3002]
MC68HC908GT8VB@SDIP42 [DX0042] MC68HC908GT8VBE@SDIP42 [DX0042]
MC68HC908GT8VFB@TQFP44 [DX3002] MC68HC908GT8VFBE@TQFP44 [DX3002]
MC68HC908GZ16CFA@TQFP48 [DX3007]
MC68HC908GZ16CFAE@TQFP48 [DX3007]
MC68HC908GZ16CFJ@TQFP32 [DX3001]
MC68HC908GZ16CFJE@TQFP32 [DX3001]
MC68HC908GZ16MFA@TQFP48 [DX3007]
MC68HC908GZ16MFAE@TQFP48 [DX3007]
MC68HC908GZ16MFJ@TQFP32 [DX3001]
MC68HC908GZ16MFJE@TQFP32 [DX3001]
MC68HC908GZ16VFA@TQFP48 [DX3007]
MC68HC908GZ16VFAE@TQFP48 [DX3007]

MC68HC908GZ16VFJ@TQFP32 [DX3001]
MC68HC908GZ16VFJE@TQFP32 [DX3001]
MC68HC908GZ32CFA@TQFP48 [DX3007]
MC68HC908GZ32CFAE@TQFP48 [DX3007]
MC68HC908GZ32CFJ@TQFP32 [DX3001]
MC68HC908GZ32CFJE@TQFP32 [DX3001]
MC68HC908GZ32CFU@QFP64 [DX3014]
MC68HC908GZ32CFUE@QFP64 [DX3014]
MC68HC908GZ32MFA@TQFP48 [DX3007]
MC68HC908GZ32MFAE@TQFP48 [DX3007]
MC68HC908GZ32MFJ@TQFP32 [DX3001]
MC68HC908GZ32MFJE@TQFP32 [DX3001]
MC68HC908GZ32MFU@QFP64 [DX3014]
MC68HC908GZ32MFUE@QFP64 [DX3014]
MC68HC908GZ32VFA@TQFP48 [DX3007]
MC68HC908GZ32VFAE@TQFP48 [DX3007]
MC68HC908GZ32VFJ@TQFP32 [DX3001]
MC68HC908GZ32VFJE@TQFP32 [DX3001]
MC68HC908GZ32VFU@QFP64 [DX3014]
MC68HC908GZ32VFUE@QFP64 [DX3014]
MC68HC908GZ48CFA@TQFP48 [DX3007]
MC68HC908GZ48CFAE@TQFP48 [DX3007]
MC68HC908GZ48CFJ@TQFP32 [DX3001]
MC68HC908GZ48CFJE@TQFP32 [DX3001]
MC68HC908GZ48CFU@QFP64 [DX3014]
MC68HC908GZ48CFUE@QFP64 [DX3014]
MC68HC908GZ48MFA@TQFP48 [DX3007]
MC68HC908GZ48MFAE@TQFP48 [DX3007]
MC68HC908GZ48MFJ@TQFP32 [DX3001]
MC68HC908GZ48MFJE@TQFP32 [DX3001]
MC68HC908GZ48MFU@QFP64 [DX3014]
MC68HC908GZ48MFUE@QFP64 [DX3014]
MC68HC908GZ48VFA@TQFP48 [DX3007]
MC68HC908GZ48VFAE@TQFP48 [DX3007]
MC68HC908GZ48VFJ@TQFP32 [DX3001]
MC68HC908GZ48VFJE@TQFP32 [DX3001]
MC68HC908GZ48VFU@QFP64 [DX3014]
MC68HC908GZ48VFUE@QFP64 [DX3014]
MC68HC908GZ60CFA@TQFP48 [DX3007]
MC68HC908GZ60CFAE@TQFP48 [DX3007]
MC68HC908GZ60CFJ@TQFP32 [DX3001]
MC68HC908GZ60CFJE@TQFP32 [DX3001]
MC68HC908GZ60CFU@QFP64 [DX3014]
MC68HC908GZ60CFUE@QFP64 [DX3014]
MC68HC908GZ60MFA@TQFP48 [DX3007]
MC68HC908GZ60MFAE@TQFP48 [DX3007]
MC68HC908GZ60MFJ@TQFP32 [DX3001]
MC68HC908GZ60MFJE@TQFP32 [DX3001]
MC68HC908GZ60MFU@QFP64 [DX3014]
MC68HC908GZ60MFUE@QFP64 [DX3014]
MC68HC908GZ60VFA@TQFP48 [DX3007]
MC68HC908GZ60VFAE@TQFP48 [DX3007]
MC68HC908GZ60VFJ@TQFP32 [DX3001]
MC68HC908GZ60VFJE@TQFP32 [DX3001]
MC68HC908GZ60VFU@QFP64 [DX3014]
MC68HC908GZ60VFUE@QFP64 [DX3014]
MC68HC908GZ8CFA@TQFP48 [DX3007]
MC68HC908GZ8CFAE@TQFP48 [DX3007]

MC68HC908GZ8CFJ@TQFP32 [DX3001]	MC68HC908GZ8CFJE@TQFP32 [DX3001]
MC68HC908GZ8MFA@TQFP48 [DX3007]	MC68HC908GZ8MFAE@TQFP48 [DX3007]
MC68HC908GZ8MFJ@TQFP32 [DX3001]	MC68HC908GZ8MFJE@TQFP32 [DX3001]
MC68HC908GZ8VFA@TQFP48 [DX3007]	MC68HC908GZ8VFAE@TQFP48 [DX3007]
MC68HC908GZ8VFJ@TQFP32 [DX3001]	MC68HC908GZ8VFJE@TQFP32 [DX3001]
MC68HC908JB12DW@SOIC28 [DX1033]	MC68HC908JB12DWE@SOIC28 [DX1033]
MC68HC908JB12JDW@SOIC20 [DX1033]	
MC68HC908JB12JDWE@SOIC20 [DX1033]	
MC68HC908JB16DW@SOIC28 [DX1033]	MC68HC908JB16DWE@SOIC28 [DX1033]
MC68HC908JB16FA@QFP32 [DX3001]	MC68HC908JB16FAE@QFP32 [DX3001]
MC68HC908JB16JDW@SOIC20 [DX1033]	
MC68HC908JB16JDWE@SOIC20 [DX1033]	
MC68HC908JB8ADW@SOIC28 [DX1033]	MC68HC908JB8ADWE@SOIC28 [DX1033]
MC68HC908JB8FB@TQFP44 [DX3003]	MC68HC908JB8FBE@TQFP44 [DX3003]
MC68HC908JB8JDW@SOIC20 [DX1033]	MC68HC908JB8JDWE@SOIC20 [DX1033]
MC68HC908JB8JP	MC68HC908JB8JPE
MC68HC908JK1CDW@SOIC20 [DX1033]	MC68HC908JK1CDWE@SOIC20 [DX1033]
MC68HC908JK1CP	MC68HC908JK1CPE
MC68HC908JK1ECDW@SOIC20 [DX1033]	
MC68HC908JK1ECDWE@SOIC20 [DX1033]	
MC68HC908JK1ECP	MC68HC908JK1ECPE
MC68HC908JK1EMDW@SOIC20 [DX1033]	
MC68HC908JK1EMDWE@SOIC20 [DX1033]	
MC68HC908JK1EMP	MC68HC908JK1EMPE
MC68HC908JK1EVDW@SOIC20 [DX1033]	
MC68HC908JK1EVDWE@SOIC20 [DX1033]	
MC68HC908JK1EVP	MC68HC908JK1EVPE
MC68HC908JK1MDW@SOIC20 [DX1033]	MC68HC908JK1MDWE@SOIC20 [DX1033]
MC68HC908JK1MP	MC68HC908JK1MPE
MC68HC908JK1VDW@SOIC20 [DX1033]	MC68HC908JK1VDWE@SOIC20 [DX1033]
MC68HC908JK1VP	MC68HC908JK1VPE
MC68HC908JK3CDW@SOIC20 [DX1033]	MC68HC908JK3CDWE@SOIC20 [DX1033]
MC68HC908JK3CP	MC68HC908JK3CPE
MC68HC908JK3ECDW@SOIC20 [DX1033]	
MC68HC908JK3ECDWE@SOIC20 [DX1033]	
MC68HC908JK3ECP	MC68HC908JK3ECPE
MC68HC908JK3EMDW@SOIC20 [DX1033]	
MC68HC908JK3EMDWE@SOIC20 [DX1033]	
MC68HC908JK3EMP	MC68HC908JK3EMPE
MC68HC908JK3EVDW@SOIC20 [DX1033]	
MC68HC908JK3EVDWE@SOIC20 [DX1033]	
MC68HC908JK3EVP	MC68HC908JK3EVPE
MC68HC908JK3MDW@SOIC20 [DX1033]	MC68HC908JK3MDWE@SOIC20 [DX1033]
MC68HC908JK3MP	MC68HC908JK3MPE
MC68HC908JK3VDW@SOIC20 [DX1033]	MC68HC908JK3VDWE@SOIC20 [DX1033]
MC68HC908JK3VP	MC68HC908JK3VPE
MC68HC908JK8CDW@SOIC20 [DX1033]	MC68HC908JK8CDWE@SOIC20 [DX1033]
MC68HC908JK8CP	MC68HC908JK8CPE

MC68HC908JK8MDW@SOIC20 [DX1033]	MC68HC908JK8MDWE@SOIC20 [DX1033]
MC68HC908JK8MP	MC68HC908JK8MPE
MC68HC908JK8VDW@SOIC20 [DX1033]	MC68HC908JK8VDWE@SOIC20 [DX1033]
MC68HC908JK8VP	MC68HC908JK8VPE
MC68HC908JL16CDW@SOIC28 [DX1033]	
MC68HC908JL16CDWE@SOIC28 [DX1033]	
MC68HC908JL16CFJ@TQFP32 [DX3001]	
MC68HC908JL16CFJE@TQFP32 [DX3001]	
MC68HC908JL16CP	MC68HC908JL16CPE
MC68HC908JL16CSP@SDIP32 [DX0032]	
MC68HC908JL16CSPE@SDIP32 [DX0032]	
MC68HC908JL16MDW@SOIC28 [DX1033]	
MC68HC908JL16MDWE@SOIC28 [DX1033]	
MC68HC908JL16MFJ@TQFP32 [DX3001]	
MC68HC908JL16MFJE@TQFP32 [DX3001]	
MC68HC908JL16MP	MC68HC908JL16MPE
MC68HC908JL16MSP@SDIP32 [DX0032]	
MC68HC908JL16MSPE@SDIP32 [DX0032]	
MC68HC908JL16VDW@SOIC28 [DX1033]	
MC68HC908JL16VDWE@SOIC28 [DX1033]	
MC68HC908JL16VFJ@TQFP32 [DX3001]	
MC68HC908JL16VFJE@TQFP32 [DX3001]	
MC68HC908JL16VP	MC68HC908JL16VPE
MC68HC908JL16VSP@SDIP32 [DX0032]	
MC68HC908JL16VSPE@SDIP32 [DX0032]	
MC68HC908JL3CDW@SOIC28 [DX1033]	MC68HC908JL3CDWE@SOIC28 [DX1033]
MC68HC908JL3CP	MC68HC908JL3CPE
MC68HC908JL3ECDW@SOIC28 [DX1033]	
MC68HC908JL3ECDWE@SOIC28 [DX1033]	
MC68HC908JL3ECFA@TQFP48 [DX3007]	
MC68HC908JL3ECFAE@TQFP48 [DX3007]	
MC68HC908JL3ECP	MC68HC908JL3ECPE
MC68HC908JL3EMDW@SOIC28 [DX1033]	
MC68HC908JL3EMDWE@SOIC28 [DX1033]	
MC68HC908JL3EMFA@TQFP48 [DX3007]	
MC68HC908JL3EMFAE@TQFP48 [DX3007]	
MC68HC908JL3EMP	MC68HC908JL3EMPE
MC68HC908JL3EVDW@SOIC28 [DX1033]	
MC68HC908JL3EVDWE@SOIC28 [DX1033]	
MC68HC908JL3EVFA@TQFP48 [DX3007]	
MC68HC908JL3EVFAE@TQFP48 [DX3007]	
MC68HC908JL3EVP	MC68HC908JL3EVPE
MC68HC908JL3MDW@SOIC28 [DX1033]	MC68HC908JL3MDWE@SOIC28 [DX1033]
MC68HC908JL3MP	MC68HC908JL3MPE
MC68HC908JL3VDW@SOIC28 [DX1033]	MC68HC908JL3VDWE@SOIC28 [DX1033]
MC68HC908JL3VP	MC68HC908JL3VPE
MC68HC908JL8CDW@SOIC28 [DX1033]	MC68HC908JL8CDWE@SOIC28 [DX1033]
MC68HC908JL8CFA@TQFP32 [DX3001]	MC68HC908JL8CFAE@TQFP32 [DX3001]

MC68HC908JL8CP
MC68HC908JL8CPE
MC68HC908JL8CSP@SDIP32 [DX0032]
MC68HC908JL8CSPE@SDIP32 [DX0032]
MC68HC908JL8MDW@SOIC28 [DX1033]
MC68HC908JL8MDWE@SOIC28 [DX1033]
MC68HC908JL8MFA@TQFP32 [DX3001]
MC68HC908JL8MFAE@TQFP32 [DX3001]
MC68HC908JL8MP
MC68HC908JL8MPE
MC68HC908JL8MSP@SDIP32 [DX0032]
MC68HC908JL8MSPE@SDIP32 [DX0032]
MC68HC908JL8VDW@SOIC28 [DX1033]
MC68HC908JL8VDWE@SOIC28 [DX1033]
MC68HC908JL8VFA@TQFP32 [DX3001]
MC68HC908JL8VFAE@TQFP32 [DX3001]
MC68HC908JL8VP
MC68HC908JL8VPE
MC68HC908JL8VSP@SDIP32 [DX0032]
MC68HC908JL8VSPE@SDIP32 [DX0032]
MC68HC908KK3ECDW@SOIC20 [DX1033]
MC68HC908KK3ECDWE@SOIC20 [DX1033]
MC68HC908KK3ECP
MC68HC908KK3ECPE
MC68HC908KK3EMDW@SOIC20 [DX1033]
MC68HC908KK3EMDWE@SOIC20 [DX1033]
MC68HC908KK3EMP
MC68HC908KK3EMPE
MC68HC908KK3EVDW@SOIC20 [DX1033]
MC68HC908KK3EVDWE@SOIC20 [DX1033]
MC68HC908KK3EVP
MC68HC908KK3EVPE
MC68HC908KL3ECDW@SOIC28 [DX1033]
MC68HC908KL3ECDWE@SOIC28 [DX1033]
MC68HC908KL3ECP
MC68HC908KL3ECPE
MC68HC908KL3EMDW@SOIC28 [DX1033]
MC68HC908KL3EMDWE@SOIC28 [DX1033]
MC68HC908KL3EMP
MC68HC908KL3EMPE
MC68HC908KL3EVDW@SOIC28 [DX1033]
MC68HC908KL3EVDWE@SOIC28 [DX1033]
MC68HC908KL3EVP
MC68HC908KL3EVPE
MC68HC908KL8CDW@SOIC28 [DX1033]
MC68HC908KL8CDWE@SOIC28 [DX1033]
MC68HC908KL8CP
MC68HC908KL8CPE
MC68HC908KL8CSP@SDIP32 [DX0032]
MC68HC908KL8CSPE@SDIP32 [DX0032]
MC68HC908KL8MDW@SOIC28 [DX1033]
MC68HC908KL8MDWE@SOIC28 [DX1033]
MC68HC908KL8MP
MC68HC908KL8MPE
MC68HC908KL8MSP@SDIP32 [DX0032]
MC68HC908KL8MSPE@SDIP32 [DX0032]
MC68HC908KL8VDW@SOIC28 [DX1033]
MC68HC908KL8VDWE@SOIC28 [DX1033]
MC68HC908KL8VP
MC68HC908KL8VPE
MC68HC908KL8VSP@SDIP32 [DX0032]
MC68HC908KL8VSPE@SDIP32 [DX0032]
MC68HC908KX2CDW@SOIC16 [DX1033]
MC68HC908KX2CDWE@SOIC16 [DX1033]
MC68HC908KX2CP
MC68HC908KX2CPE
MC68HC908KX2MDW@SOIC16 [DX1033]
MC68HC908KX2MDWE@SOIC16 [DX1033]
MC68HC908KX2MP
MC68HC908KX2MPE
MC68HC908KX2VDW@SOIC16 [DX1033]
MC68HC908KX2VDWE@SOIC16 [DX1033]
MC68HC908KX8CDW@SOIC16 [DX1033]
MC68HC908KX8CDWE@SOIC16 [DX1033]
MC68HC908KX8CP
MC68HC908KX8CPE
MC68HC908KX8MDW@SOIC16 [DX1033]
MC68HC908KX8MDWE@SOIC16 [DX1033]
MC68HC908KX8MP
MC68HC908KX8MPE
MC68HC908KX8VDW@SOIC16 [DX1033]
MC68HC908KX8VDWE@SOIC16 [DX1033]
MC68HC908KX8VP
MC68HC908KX8VPE

MC68HC908KXVMP
MC68HC908KXVMPE
MC68HC908LB8CDW@SOIC20 [DX1033]
MC68HC908LB8CDWE@SOIC20 [DX1033]
MC68HC908LB8CP
MC68HC908LB8CPE
MC68HC908LB8MDW@SOIC20 [DX1033]
MC68HC908LB8MDWE@SOIC20 [DX1033]
MC68HC908LB8MP
MC68HC908LB8MPE
MC68HC908LB8VDW@SOIC20 [DX1033]
MC68HC908LB8VDWE@SOIC20 [DX1033]
MC68HC908LB8VP
MC68HC908LB8VPE
MC68HC908LD60IFU@QFP64 [DX3014]
MC68HC908LD64IFU@QFP64 [DX3014]
MC68HC908LJ12CFB@TQFP52 [DX3010]
MC68HC908LJ12CFBE@TQFP52 [DX3010]
MC68HC908LJ12CFU@TQFP64 [DX3014]
MC68HC908LJ12CFUE@TQFP64 [DX3014]
MC68HC908LJ12CPB@TQFP64 [DX3011]
MC68HC908LJ12CPBE@TQFP64 [DX3011]
MC68HC908LJ12MFB@TQFP52 [DX3010]
MC68HC908LJ12MFBE@TQFP52 [DX3010]
MC68HC908LJ12MFU@TQFP64 [DX3014]
MC68HC908LJ12MFUE@TQFP64 [DX3014]
MC68HC908LJ12MPB@TQFP64 [DX3011]
MC68HC908LJ12MPBE@TQFP64 [DX3011]
MC68HC908LJ12VFB@TQFP52 [DX3010]
MC68HC908LJ12VFBE@TQFP52 [DX3010]
MC68HC908LJ12VFU@TQFP64 [DX3014]
MC68HC908LJ12VFUE@TQFP64 [DX3014]
MC68HC908LJ12VPB@TQFP64 [DX3011]
MC68HC908LJ12VPBE@TQFP64 [DX3011]
MC68HC908LJ24CFQ@TQFP80 [DX3018]
MC68HC908LJ24CFQE@TQFP80 [DX3018]
MC68HC908LJ24CFU@TQFP64 [DX3014]
MC68HC908LJ24CFUE@TQFP64 [DX3014]
MC68HC908LJ24CPB@TQFP64 [DX3011]
MC68HC908LJ24CPBE@TQFP64 [DX3011]
MC68HC908LJ24CPK@TQFP80 [DX3016]
MC68HC908LJ24CPKE@TQFP80 [DX3016]
MC68HC908LJ24MFQ@TQFP80 [DX3018]
MC68HC908LJ24MFQE@TQFP80 [DX3018]
MC68HC908LJ24MFU@TQFP64 [DX3014]
MC68HC908LJ24MFUE@TQFP64 [DX3014]
MC68HC908LJ24MPB@TQFP64 [DX3011]
MC68HC908LJ24MPBE@TQFP64 [DX3011]
MC68HC908LJ24MPK@TQFP80 [DX3016]
MC68HC908LJ24MPKE@TQFP80 [DX3016]
MC68HC908LJ24VFQ@TQFP80 [DX3018]
MC68HC908LJ24VFQE@TQFP80 [DX3018]
MC68HC908LJ24VFU@TQFP64 [DX3014]
MC68HC908LJ24VFUE@TQFP64 [DX3014]
MC68HC908LJ24VPB@TQFP64 [DX3011]
MC68HC908LJ24VPBE@TQFP64 [DX3011]

MC68HC908LJ24VPK@TQFP80 [DX3016]
MC68HC908LJ24VPKE@TQFP80 [DX3016]
MC68HC908LK24CFQ@TQFP80 [DX3018]
MC68HC908LK24CFQE@TQFP80 [DX3018]
MC68HC908LK24CFU@TQFP64 [DX3014]
MC68HC908LK24CFUE@TQFP64 [DX3014]
MC68HC908LK24CPB@TQFP64 [DX3011]
MC68HC908LK24CPBE@TQFP64 [DX3011]
MC68HC908LK24CPK@TQFP80 [DX3016]
MC68HC908LK24CPKE@TQFP80 [DX3016]
MC68HC908LK24MFQ@TQFP80 [DX3018]
MC68HC908LK24MFQE@TQFP80 [DX3018]
MC68HC908LK24MFU@TQFP64 [DX3014]
MC68HC908LK24MFUE@TQFP64 [DX3014]
MC68HC908LK24MPB@TQFP64 [DX3011]
MC68HC908LK24MPBE@TQFP64 [DX3011]
MC68HC908LK24MPK@TQFP80 [DX3016]
MC68HC908LK24MPKE@TQFP80 [DX3016]
MC68HC908LK24VFQ@TQFP80 [DX3018]
MC68HC908LK24VFQE@TQFP80 [DX3018]
MC68HC908LK24VFU@TQFP64 [DX3014]
MC68HC908LK24VFUE@TQFP64 [DX3014]
MC68HC908LK24VPB@TQFP64 [DX3011]
MC68HC908LK24VPBE@TQFP64 [DX3011]
MC68HC908LK24VPK@TQFP80 [DX3016]
MC68HC908LK24VPKE@TQFP80 [DX3016]
MC68HC908LV8CPB@TQFP52 [DX3010] MC68HC908LV8CPBE@TQFP52 [DX3010]
MC68HC908MR16CB@SDIP56 [DX0056] MC68HC908MR16CBE@SDIP56 [DX0056]
MC68HC908MR16CFU@TQFP64 [DX3014]
MC68HC908MR16CFUE@TQFP64 [DX3014]
MC68HC908MR16MB@SDIP56 [DX0056] MC68HC908MR16MBE@SDIP56 [DX0056]
MC68HC908MR16MFU@TQFP64 [DX3014]
MC68HC908MR16MFUE@TQFP64 [DX3014]
MC68HC908MR16VB@SDIP56 [DX0056] MC68HC908MR16VBE@SDIP56 [DX0056]
MC68HC908MR16VFU@TQFP64 [DX3014]
MC68HC908MR16VFUE@TQFP64 [DX3014]
MC68HC908MR32CB@SDIP56 [DX0056] MC68HC908MR32CBE@SDIP56 [DX0056]
MC68HC908MR32CFU@TQFP64 [DX3014]
MC68HC908MR32CFUE@TQFP64 [DX3014]
MC68HC908MR32MB@SDIP56 [DX0056] MC68HC908MR32MBE@SDIP56 [DX0056]
MC68HC908MR32MFU@TQFP64 [DX3014]
MC68HC908MR32MFUE@TQFP64 [DX3014]
MC68HC908MR32VB@SDIP56 [DX0056] MC68HC908MR32VBE@SDIP56 [DX0056]
MC68HC908MR32VFU@TQFP64 [DX3014]
MC68HC908MR32VFUE@TQFP64 [DX3014]
MC68HC908MR8CDW@SOIC28 [DX1033] MC68HC908MR8CDWE@SOIC28 [DX1033]
MC68HC908MR8CFA@QFP32 [DX3001] MC68HC908MR8CFAE@QFP32 [DX3001]
MC68HC908MR8CP MC68HC908MR8CPE

MC68HC908MR8MDW@SOIC28 [DX1033]
MC68HC908MR8MDWE@SOIC28 [DX1033]
MC68HC908MR8MFA@QFP32 [DX3001]
MC68HC908MR8MFAE@QFP32 [DX3001]
MC68HC908MR8MP
MC68HC908MR8MPE
MC68HC908MR8VDW@SOIC28 [DX1033]
MC68HC908MR8VDWE@SOIC28 [DX1033]
MC68HC908MR8VFA@QFP32 [DX3001]
MC68HC908MR8VFAE@QFP32 [DX3001]
MC68HC908MR8VP
MC68HC908MR8VPE
MC68HC908QB4CDT@TSSOP16 [DX1001]
MC68HC908QB4CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB4CDTE@TSSOP16 [DX1001]
MC68HC908QB4CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4CDW@SOIC16 [DX1072]
MC68HC908QB4CDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4CDWE@SOIC16 [DX1072]
MC68HC908QB4CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4CP
MC68HC908QB4CP(a-trim)
MC68HC908QB4CPE
MC68HC908QB4CPE(a-trim)
MC68HC908QB4MDT@TSSOP16 [DX1001]
MC68HC908QB4MDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB4MDTE@TSSOP16 [DX1001]
MC68HC908QB4MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4MDW@SOIC16 [DX1072]
MC68HC908QB4MDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4MDWE@SOIC16 [DX1072]
MC68HC908QB4MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4MP
MC68HC908QB4MP(a-trim)
MC68HC908QB4MPE
MC68HC908QB4MPE(a-trim)
MC68HC908QB4VDT@TSSOP16 [DX1001]
MC68HC908QB4VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB4VDTE@TSSOP16 [DX1001]
MC68HC908QB4VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB4VDW@SOIC16 [DX1072]
MC68HC908QB4VDW@SOIC16(a-trim) [DX1072]
MC68HC908QB4VDWE@SOIC16 [DX1072]
MC68HC908QB4VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB4VP
MC68HC908QB4VP(a-trim)
MC68HC908QB4VPE
MC68HC908QB4VPE(a-trim)
MC68HC908QB8CDT@TSSOP16 [DX1001]
MC68HC908QB8CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB8CDTE@TSSOP16 [DX1001]
MC68HC908QB8CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8CDW@SOIC16 [DX1072]
MC68HC908QB8CDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8CDWE@SOIC16 [DX1072]
MC68HC908QB8CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8CP
MC68HC908QB8CP(a-trim)
MC68HC908QB8CPE
MC68HC908QB8CPE(a-trim)
MC68HC908QB8MDT@TSSOP16 [DX1001]
MC68HC908QB8MDT@TSSOP16(a-trim) [DX1001]

MC68HC908QB8MDTE@TSSOP16 [DX1001]
MC68HC908QB8MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8MDW@SOIC16 [DX1072]
MC68HC908QB8MDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8MDWE@SOIC16 [DX1072]
MC68HC908QB8MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8MP MC68HC908QB8MP(a-trim)
MC68HC908QB8MPE MC68HC908QB8MPE(a-trim)
MC68HC908QB8VDT@TSSOP16 [DX1001]
MC68HC908QB8VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QB8VDTE@TSSOP16 [DX1001]
MC68HC908QB8VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QB8VDW@SOIC16 [DX1072]
MC68HC908QB8VDW@SOIC16(a-trim) [DX1072]
MC68HC908QB8VDWE@SOIC16 [DX1072]
MC68HC908QB8VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QB8VP MC68HC908QB8VP(a-trim)
MC68HC908QB8VPE MC68HC908QB8VPE(a-trim)
MC68HC908QC16CDR@TSSOP28 [DX1001]
MC68HC908QC16CDRE@TSSOP28 [DX1001]
MC68HC908QC16CDS@TSSOP20 [DX1001]
MC68HC908QC16CDSE@TSSOP20 [DX1001]
MC68HC908QC16CDT@TSSOP16 [DX1001]
MC68HC908QC16CDTE@TSSOP16 [DX1001]
MC68HC908QC16CDX@SOIC16 [DX1072]
MC68HC908QC16CDXE@SOIC16 [DX1072]
MC68HC908QC16CDY@SOIC20 [DX1033]
MC68HC908QC16CDYE@SOIC20 [DX1033]
MC68HC908QC16CDZ@SOIC28 [DX1033]
MC68HC908QC16CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16CDZE@SOIC28 [DX1033]
MC68HC908QC16CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC16MDR@TSSOP28 [DX1001]
MC68HC908QC16MDRE@TSSOP28 [DX1001]
MC68HC908QC16MDS@TSSOP20 [DX1001]
MC68HC908QC16MDSE@TSSOP20 [DX1001]
MC68HC908QC16MDT@TSSOP16 [DX1001]
MC68HC908QC16MDTE@TSSOP16 [DX1001]
MC68HC908QC16MDX@SOIC16 [DX1072]
MC68HC908QC16MDXE@SOIC16 [DX1072]
MC68HC908QC16MDY@SOIC20 [DX1033]
MC68HC908QC16MDYE@SOIC20 [DX1033]
MC68HC908QC16MDZ@SOIC28 [DX1033]
MC68HC908QC16MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16MDZE@SOIC28 [DX1033]
MC68HC908QC16MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC16VDR@TSSOP28 [DX1001]
MC68HC908QC16VDRE@TSSOP28 [DX1001]

MC68HC908QC16VDS@TSSOP20 [DX1001]
MC68HC908QC16VDSE@TSSOP20 [DX1001]
MC68HC908QC16VDT@TSSOP16 [DX1001]
MC68HC908QC16VDTE@TSSOP16 [DX1001]
MC68HC908QC16VDX@SOIC16 [DX1072]
MC68HC908QC16VDXE@SOIC16 [DX1072]
MC68HC908QC16VDY@SOIC20 [DX1033]
MC68HC908QC16VDYE@SOIC20 [DX1033]
MC68HC908QC16VDZ@SOIC28 [DX1033]
MC68HC908QC16VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC16VDZE@SOIC28 [DX1033]
MC68HC908QC16VDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4CDR@TSSOP28 [DX1001]
MC68HC908QC4CDRE@TSSOP28 [DX1001]
MC68HC908QC4CDS@TSSOP20 [DX1001]
MC68HC908QC4CDSE@TSSOP20 [DX1001]
MC68HC908QC4CDT@TSSOP16 [DX1001]
MC68HC908QC4CDTE@TSSOP16 [DX1001]
MC68HC908QC4CDX@SOIC16 [DX1072]　　MC68HC908QC4CDXE@SOIC16 [DX1072]
MC68HC908QC4CDY@SOIC20 [DX1033]　　MC68HC908QC4CDYE@SOIC20 [DX1033]
MC68HC908QC4CDZ@SOIC28 [DX1033]
MC68HC908QC4CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4CDZE@SOIC28 [DX1033]
MC68HC908QC4CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4MDR@TSSOP28 [DX1001]
MC68HC908QC4MDRE@TSSOP28 [DX1001]
MC68HC908QC4MDS@TSSOP20 [DX1001]
MC68HC908QC4MDSE@TSSOP20 [DX1001]
MC68HC908QC4MDT@TSSOP16 [DX1001]
MC68HC908QC4MDTE@TSSOP16 [DX1001]
MC68HC908QC4MDX@SOIC16 [DX1072]　　MC68HC908QC4MDXE@SOIC16 [DX1072]
MC68HC908QC4MDY@SOIC20 [DX1033]　　MC68HC908QC4MDYE@SOIC20 [DX1033]
MC68HC908QC4MDZ@SOIC28 [DX1033]
MC68HC908QC4MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4MDZE@SOIC28 [DX1033]
MC68HC908QC4MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC4VDR@TSSOP28 [DX1001]
MC68HC908QC4VDRE@TSSOP28 [DX1001]
MC68HC908QC4VDS@TSSOP20 [DX1001]
MC68HC908QC4VDSE@TSSOP20 [DX1001]
MC68HC908QC4VDT@TSSOP16 [DX1001]
MC68HC908QC4VDTE@TSSOP16 [DX1001]
MC68HC908QC4VDX@SOIC16 [DX1072]　　MC68HC908QC4VDXE@SOIC16 [DX1072]
MC68HC908QC4VDY@SOIC20 [DX1033]　　MC68HC908QC4VDYE@SOIC20 [DX1033]
MC68HC908QC4VDZ@SOIC28 [DX1033]
MC68HC908QC4VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC4VDZE@SOIC28 [DX1033]
MC68HC908QC4VDZE@SOIC28(a-trim) [DX1033]

MC68HC908QC8CDR@TSSOP28 [DX1001]
MC68HC908QC8CDRE@TSSOP28 [DX1001]
MC68HC908QC8CDS@TSSOP20 [DX1001]
MC68HC908QC8CDSE@TSSOP20 [DX1001]
MC68HC908QC8CDT@TSSOP16 [DX1001]
MC68HC908QC8CDTE@TSSOP16 [DX1001]
MC68HC908QC8CDX@SOIC16 [DX1072]　　MC68HC908QC8CDXE@SOIC16 [DX1072]
MC68HC908QC8CDY@SOIC20 [DX1033]　　MC68HC908QC8CDYE@SOIC20 [DX1033]
MC68HC908QC8CDZ@SOIC28 [DX1033]
MC68HC908QC8CDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8CDZE@SOIC28 [DX1033]
MC68HC908QC8CDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC8MDR@TSSOP28 [DX1001]
MC68HC908QC8MDRE@TSSOP28 [DX1001]
MC68HC908QC8MDS@TSSOP20 [DX1001]
MC68HC908QC8MDSE@TSSOP20 [DX1001]
MC68HC908QC8MDT@TSSOP16 [DX1001]
MC68HC908QC8MDTE@TSSOP16 [DX1001]
MC68HC908QC8MDX@SOIC16 [DX1072]　　MC68HC908QC8MDXE@SOIC16 [DX1072]
MC68HC908QC8MDY@SOIC20 [DX1033]　　MC68HC908QC8MDYE@SOIC20 [DX1033]
MC68HC908QC8MDZ@SOIC28 [DX1033]
MC68HC908QC8MDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8MDZE@SOIC28 [DX1033]
MC68HC908QC8MDZE@SOIC28(a-trim) [DX1033]
MC68HC908QC8VDR@TSSOP28 [DX1001]
MC68HC908QC8VDRE@TSSOP28 [DX1001]
MC68HC908QC8VDS@TSSOP20 [DX1001]
MC68HC908QC8VDSE@TSSOP20 [DX1001]
MC68HC908QC8VDT@TSSOP16 [DX1001]
MC68HC908QC8VDTE@TSSOP16 [DX1001]
MC68HC908QC8VDX@SOIC16 [DX1072]　　MC68HC908QC8VDXE@SOIC16 [DX1072]
MC68HC908QC8VDY@SOIC20 [DX1033]　　MC68HC908QC8VDYE@SOIC20 [DX1033]
MC68HC908QC8VDZ@SOIC28 [DX1033]
MC68HC908QC8VDZ@SOIC28(a-trim) [DX1033]
MC68HC908QC8VDZE@SOIC28 [DX1033]
MC68HC908QC8VDZE@SOIC28(a-trim) [DX1033]
MC68HC908QF4CFJ@QFP32 [DX3001]　　MC68HC908QF4CFJE@QFP32 [DX3001]
MC68HC908QF4MFJ@QFP32 [DX3001]　　MC68HC908QF4MFJE@QFP32 [DX3001]
MC68HC908QF4VFJ@QFP32 [DX3001]　　MC68HC908QF4VFJE@QFP32 [DX3001]
MC68HC908QL2CDT@TSSOP16 [DX1001]
MC68HC908QL2CDTE@TSSOP16 [DX1001]
MC68HC908QL2CDW@SOIC16 [DX1032]　　MC68HC908QL2CDWE@SOIC16 [DX1032]
MC68HC908QL2MDT@TSSOP16 [DX1001]
MC68HC908QL2MDTE@TSSOP16 [DX1001]
MC68HC908QL2MDW@SOIC16 [DX1032]　　MC68HC908QL2MDWE@SOIC16 [DX1032]
MC68HC908QL2VDT@TSSOP16 [DX1001]
MC68HC908QL2VDTE@TSSOP16 [DX1001]
MC68HC908QL2VDW@SOIC16 [DX1032]　　MC68HC908QL2VDWE@SOIC16 [DX1032]

MC68HC908QL3CDT@TSSOP16 [DX1001]
MC68HC908QL3CDTE@TSSOP16 [DX1001]
MC68HC908QL3CDW@SOIC16 [DX1032] MC68HC908QL3CDWE@SOIC16 [DX1032]
MC68HC908QL3MDT@TSSOP16 [DX1001]
MC68HC908QL3MDTE@TSSOP16 [DX1001]
MC68HC908QL3MDW@SOIC16 [DX1032] MC68HC908QL3MDWE@SOIC16 [DX1032]
MC68HC908QL3VDT@TSSOP16 [DX1001]
MC68HC908QL3VDTE@TSSOP16 [DX1001]
MC68HC908QL3VDW@SOIC16 [DX1032] MC68HC908QL3VDWE@SOIC16 [DX1032]
MC68HC908QL4CDT@TSSOP16 [DX1001]
MC68HC908QL4CDTE@TSSOP16 [DX1001]
MC68HC908QL4CDW@SOIC16 [DX1032] MC68HC908QL4CDWE@SOIC16 [DX1032]
MC68HC908QL4MDT@TSSOP16 [DX1001]
MC68HC908QL4MDTE@TSSOP16 [DX1001]
MC68HC908QL4MDW@SOIC16 [DX1032] MC68HC908QL4MDWE@SOIC16 [DX1032]
MC68HC908QL4VDT@TSSOP16 [DX1001]
MC68HC908QL4VDTE@TSSOP16 [DX1001]
MC68HC908QL4VDW@SOIC16 [DX1032] MC68HC908QL4VDWE@SOIC16 [DX1032]
MC68HC908QT1ACDW@SOIC8 [DX1032]
MC68HC908QT1ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1ACDWE@SOIC8 [DX1032]
MC68HC908QT1ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1ACFQ@DFN8 [DX4004]
MC68HC908QT1ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1ACFQE@DFN8 [DX4004]
MC68HC908QT1ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1ACP MC68HC908QT1ACP(a-trim)
MC68HC908QT1ACPE MC68HC908QT1ACPE(a-trim)
MC68HC908QT1AMDW@SOIC8 [DX1032]
MC68HC908QT1AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1AMDWE@SOIC8 [DX1032]
MC68HC908QT1AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1AMFQ@DFN8 [DX4004]
MC68HC908QT1AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1AMFQE@DFN8 [DX4004]
MC68HC908QT1AMFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1AMP MC68HC908QT1AMP(a-trim)
MC68HC908QT1AMPE MC68HC908QT1AMPE(a-trim)
MC68HC908QT1AVDW@SOIC8 [DX1032]
MC68HC908QT1AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT1AVDWE@SOIC8 [DX1032]
MC68HC908QT1AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT1AVFQ@DFN8 [DX4004]
MC68HC908QT1AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT1AVFQE@DFN8 [DX4004]
MC68HC908QT1AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT1AVP MC68HC908QT1AVP(a-trim)
MC68HC908QT1AVPE MC68HC908QT1AVPE(a-trim)

MC68HC908QT1CDW@SOIC8 [DX1032]
MC68HC908QT1CDWE@SOIC8 [DX1032]
MC68HC908QT1CFQ@DFN8 [DX4004]
MC68HC908QT1CFQE@DFN8 [DX4004]
MC68HC908QT1CP
MC68HC908QT1CPE
MC68HC908QT1MDW@SOIC8 [DX1032]
MC68HC908QT1MDWE@SOIC8 [DX1032]
MC68HC908QT1MFQ@DFN8 [DX4004]
MC68HC908QT1MFQE@DFN8 [DX4004]
MC68HC908QT1MP
MC68HC908QT1MPE
MC68HC908QT1VDW@SOIC8 [DX1032]
MC68HC908QT1VDWE@SOIC8 [DX1032]
MC68HC908QT1VFQ@DFN8 [DX4004]
MC68HC908QT1VFQE@DFN8 [DX4004]
MC68HC908QT1VP
MC68HC908QT1VPE
MC68HC908QT2ACDW@SOIC8 [DX1032]
MC68HC908QT2ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2ACDWE@SOIC8 [DX1032]
MC68HC908QT2ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2ACFQ@DFN8 [DX4004]
MC68HC908QT2ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2ACFQE@DFN8 [DX4004]
MC68HC908QT2ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2ACP
MC68HC908QT2ACP(a-trim)
MC68HC908QT2ACPE
MC68HC908QT2ACPE(a-trim)
MC68HC908QT2AMDW@SOIC8 [DX1032]
MC68HC908QT2AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2AMDWE@SOIC8 [DX1032]
MC68HC908QT2AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2AMFQ@DFN8 [DX4004]
MC68HC908QT2AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2AMFQE@DFN8 [DX4004]
MC68HC908QT2AMFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2AMP
MC68HC908QT2AMP(a-trim)
MC68HC908QT2AMPE
MC68HC908QT2AMPE(a-trim)
MC68HC908QT2AVDW@SOIC8 [DX1032]
MC68HC908QT2AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT2AVDWE@SOIC8 [DX1032]
MC68HC908QT2AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT2AVFQ@DFN8 [DX4004]
MC68HC908QT2AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT2AVFQE@DFN8 [DX4004]
MC68HC908QT2AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT2AVP
MC68HC908QT2AVP(a-trim)
MC68HC908QT2AVPE
MC68HC908QT2AVPE(a-trim)
MC68HC908QT2CDW@SOIC8 [DX1032]
MC68HC908QT2CDWE@SOIC8 [DX1032]
MC68HC908QT2CFQ@DFN8 [DX4004]
MC68HC908QT2CFQE@DFN8 [DX4004]
MC68HC908QT2CP
MC68HC908QT2CPE
MC68HC908QT2MDW@SOIC8 [DX1032]
MC68HC908QT2MDWE@SOIC8 [DX1032]
MC68HC908QT2MFQ@DFN8 [DX4004]
MC68HC908QT2MFQE@DFN8 [DX4004]
MC68HC908QT2MP
MC68HC908QT2MPE
MC68HC908QT2VDW@SOIC8 [DX1032]
MC68HC908QT2VDWE@SOIC8 [DX1032]
MC68HC908QT2VFQ@DFN8 [DX4004]
MC68HC908QT2VFQE@DFN8 [DX4004]
MC68HC908QT2VP
MC68HC908QT2VPE

MC68HC908QT4ACDW@SOIC8 [DX1032]
MC68HC908QT4ACDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4ACDWE@SOIC8 [DX1032]
MC68HC908QT4ACDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4ACFQ@DFN8 [DX4004]
MC68HC908QT4ACFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4ACFQE@DFN8 [DX4004]
MC68HC908QT4ACFQE@DFN8(a-trim) [DX4004]
MC68HC908QT4ACP MC68HC908QT4ACP(a-trim)
MC68HC908QT4ACPE MC68HC908QT4ACPE(a-trim)
MC68HC908QT4AMDW@SOIC8 [DX1032]
MC68HC908QT4AMDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4AMDWE@SOIC8 [DX1032]
MC68HC908QT4AMDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4AMFQ@DFN8 [DX4004]
MC68HC908QT4AMFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4AMFQE@DFN8 [DX4004]
MC68HC908QT4AMFQE@DFN8(a-trim) [DX4004]
MC68HC908QT4AMP MC68HC908QT4AMP(a-trim)
MC68HC908QT4AMPE MC68HC908QT4AMPE(a-trim)
MC68HC908QT4AVDW@SOIC8 [DX1032]
MC68HC908QT4AVDW@SOIC8(a-trim) [DX1032]
MC68HC908QT4AVDWE@SOIC8 [DX1032]
MC68HC908QT4AVDWE@SOIC8(a-trim) [DX1032]
MC68HC908QT4AVFQ@DFN8 [DX4004]
MC68HC908QT4AVFQ@DFN8(a-trim) [DX4004]
MC68HC908QT4AVFQE@DFN8 [DX4004]
MC68HC908QT4AVFQE@DFN8(a-trim) [DX4004]
MC68HC908QT4AVP MC68HC908QT4AVP(a-trim)
MC68HC908QT4AVPE MC68HC908QT4AVPE(a-trim)
MC68HC908QT4CDW@SOIC8 [DX1032] MC68HC908QT4CDWE@SOIC8 [DX1032]
MC68HC908QT4CFQ@DFN8 [DX4004] MC68HC908QT4CFQE@DFN8 [DX4004]
MC68HC908QT4CP MC68HC908QT4CPE
MC68HC908QT4MDW@SOIC8 [DX1032] MC68HC908QT4MDWE@SOIC8 [DX1032]
MC68HC908QT4MFQ@DFN8 [DX4004] MC68HC908QT4MFQE@DFN8 [DX4004]
MC68HC908QT4MP MC68HC908QT4MPE
MC68HC908QT4VDW@SOIC8 [DX1032] MC68HC908QT4VDWE@SOIC8 [DX1032]
MC68HC908QT4VFQ@DFN8 [DX4004] MC68HC908QT4VFQE@DFN8 [DX4004]
MC68HC908QT4VP MC68HC908QT4VPE
MC68HC908QY1ACDT@TSSOP16 [DX1001]
MC68HC908QY1ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1ACDTE@TSSOP16 [DX1001]
MC68HC908QY1ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1ACDW@SOIC16 [DX1072]
MC68HC908QY1ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1ACDWE@SOIC16 [DX1072]
MC68HC908QY1ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1ACP MC68HC908QY1ACP(a-trim)

MC68HC908QY1ACPE MC68HC908QY1ACPE(a-trim)
MC68HC908QY1AMDT@TSSOP16 [DX1001]
MC68HC908QY1AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1AMDTE@TSSOP16 [DX1001]
MC68HC908QY1AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1AMDW@SOIC16 [DX1072]
MC68HC908QY1AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1AMDWE@SOIC16 [DX1072]
MC68HC908QY1AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1AMP MC68HC908QY1AMP(a-trim)
MC68HC908QY1AMPE MC68HC908QY1AMPE(a-trim)
MC68HC908QY1AVDT@TSSOP16 [DX1001]
MC68HC908QY1AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY1AVDTE@TSSOP16 [DX1001]
MC68HC908QY1AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY1AVDW@SOIC16 [DX1072]
MC68HC908QY1AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY1AVDWE@SOIC16 [DX1072]
MC68HC908QY1AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY1AVP MC68HC908QY1AVP(a-trim)
MC68HC908QY1AVPE MC68HC908QY1AVPE(a-trim)
MC68HC908QY1CDT@TSSOP16 [DX1001]
MC68HC908QY1CDTE@TSSOP16 [DX1001]
MC68HC908QY1CDW@SOIC16 [DX1072] MC68HC908QY1CDWE@SOIC16 [DX1072]
MC68HC908QY1CP MC68HC908QY1CPE
MC68HC908QY1MDT@TSSOP16 [DX1001]
MC68HC908QY1MDTE@TSSOP16 [DX1001]
MC68HC908QY1MDW@SOIC16 [DX1072] MC68HC908QY1MDWE@SOIC16 [DX1072]
MC68HC908QY1MP MC68HC908QY1MPE
MC68HC908QY1VDT@TSSOP16 [DX1001]
MC68HC908QY1VDTE@TSSOP16 [DX1001]
MC68HC908QY1VDW@SOIC16 [DX1072] MC68HC908QY1VDWE@SOIC16 [DX1072]
MC68HC908QY1VP MC68HC908QY1VPE
MC68HC908QY2ACDT@TSSOP16 [DX1001]
MC68HC908QY2ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2ACDTE@TSSOP16 [DX1001]
MC68HC908QY2ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2ACDW@SOIC16 [DX1072]
MC68HC908QY2ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2ACDWE@SOIC16 [DX1072]
MC68HC908QY2ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2ACP MC68HC908QY2ACP(a-trim)
MC68HC908QY2ACPE MC68HC908QY2ACPE(a-trim)
MC68HC908QY2AMDT@TSSOP16 [DX1001]
MC68HC908QY2AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2AMDTE@TSSOP16 [DX1001]
MC68HC908QY2AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2AMDW@SOIC16 [DX1072]

MC68HC908QY2AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2AMDWE@SOIC16 [DX1072]
MC68HC908QY2AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2AMP MC68HC908QY2AMP(a-trim)
MC68HC908QY2AMPE MC68HC908QY2AMPE(a-trim)
MC68HC908QY2AVDT@TSSOP16 [DX1001]
MC68HC908QY2AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY2AVDTE@TSSOP16 [DX1001]
MC68HC908QY2AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY2AVDW@SOIC16 [DX1072]
MC68HC908QY2AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY2AVDWE@SOIC16 [DX1072]
MC68HC908QY2AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY2AVP MC68HC908QY2AVP(a-trim)
MC68HC908QY2AVPE MC68HC908QY2AVPE(a-trim)
MC68HC908QY2CDT@TSSOP16 [DX1001]
MC68HC908QY2CDTE@TSSOP16 [DX1001]
MC68HC908QY2CDW@SOIC16 [DX1072] MC68HC908QY2CDWE@SOIC16 [DX1072]
MC68HC908QY2CP MC68HC908QY2CPE
MC68HC908QY2MDT@TSSOP16 [DX1001]
MC68HC908QY2MDTE@TSSOP16 [DX1001]
MC68HC908QY2MDW@SOIC16 [DX1072] MC68HC908QY2MDWE@SOIC16 [DX1072]
MC68HC908QY2MP MC68HC908QY2MPE
MC68HC908QY2VDT@TSSOP16 [DX1001]
MC68HC908QY2VDTE@TSSOP16 [DX1001]
MC68HC908QY2VDW@SOIC16 [DX1072] MC68HC908QY2VDWE@SOIC16 [DX1072]
MC68HC908QY2VP MC68HC908QY2VPE
MC68HC908QY4ACDT@TSSOP16 [DX1001]
MC68HC908QY4ACDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4ACDTE@TSSOP16 [DX1001]
MC68HC908QY4ACDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4ACDW@SOIC16 [DX1072]
MC68HC908QY4ACDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4ACDWE@SOIC16 [DX1072]
MC68HC908QY4ACDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4ACP MC68HC908QY4ACP(a-trim)
MC68HC908QY4ACPE MC68HC908QY4ACPE(a-trim)
MC68HC908QY4AMDT@TSSOP16 [DX1001]
MC68HC908QY4AMDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4AMDTE@TSSOP16 [DX1001]
MC68HC908QY4AMDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4AMDW@SOIC16 [DX1072]
MC68HC908QY4AMDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4AMDWE@SOIC16 [DX1072]
MC68HC908QY4AMDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4AMP MC68HC908QY4AMP(a-trim)
MC68HC908QY4AMPE MC68HC908QY4AMPE(a-trim)
MC68HC908QY4AVDT@TSSOP16 [DX1001]

MC68HC908QY4AVDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY4AVDTE@TSSOP16 [DX1001]
MC68HC908QY4AVDTE@TSSOP16(atrim) [DX1001]
MC68HC908QY4AVDW@SOIC16 [DX1072]
MC68HC908QY4AVDW@SOIC16(a-trim) [DX1072]
MC68HC908QY4AVDWE@SOIC16 [DX1072]
MC68HC908QY4AVDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY4AVP MC68HC908QY4AVP(a-trim)
MC68HC908QY4AVPE MC68HC908QY4AVPE(a-trim)
MC68HC908QY4CDT@TSSOP16 [DX1001]
MC68HC908QY4CDTE@TSSOP16 [DX1001]
MC68HC908QY4CDW@SOIC16 [DX1072] MC68HC908QY4CDWE@SOIC16 [DX1072]
MC68HC908QY4CP MC68HC908QY4CPE
MC68HC908QY4MDT@TSSOP16 [DX1001]
MC68HC908QY4MDTE@TSSOP16 [DX1001]
MC68HC908QY4MDW@SOIC16 [DX1072] MC68HC908QY4MDWE@SOIC16 [DX1072]
MC68HC908QY4MP MC68HC908QY4MPE
MC68HC908QY4VDT@TSSOP16 [DX1001]
MC68HC908QY4VDTE@TSSOP16 [DX1001]
MC68HC908QY4VDW@SOIC16 [DX1072] MC68HC908QY4VDWE@SOIC16 [DX1072]
MC68HC908QY4VP MC68HC908QY4VPE
MC68HC908QY8CDT@TSSOP16 [DX1001]
MC68HC908QY8CDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8CDTE@TSSOP16 [DX1001]
MC68HC908QY8CDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8CDW@SOIC16 [DX1072]
MC68HC908QY8CDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8CDWE@SOIC16 [DX1072]
MC68HC908QY8CDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8CP MC68HC908QY8CP(a-trim)
MC68HC908QY8CPE MC68HC908QY8CPE(a-trim)
MC68HC908QY8MDT@TSSOP16 [DX1001]
MC68HC908QY8MDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8MDTE@TSSOP16 [DX1001]
MC68HC908QY8MDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8MDW@SOIC16 [DX1072]
MC68HC908QY8MDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8MDWE@SOIC16 [DX1072]
MC68HC908QY8MDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8MP MC68HC908QY8MP(a-trim)
MC68HC908QY8MPE MC68HC908QY8MPE(a-trim)
MC68HC908QY8VDT@TSSOP16 [DX1001]
MC68HC908QY8VDT@TSSOP16(a-trim) [DX1001]
MC68HC908QY8VDTE@TSSOP16 [DX1001]
MC68HC908QY8VDTE@TSSOP16(a-trim) [DX1001]
MC68HC908QY8VDW@SOIC16 [DX1072]
MC68HC908QY8VDW@SOIC16(a-trim) [DX1072]
MC68HC908QY8VDWE@SOIC16 [DX1072]

MC68HC908QY8VDWE@SOIC16(a-trim) [DX1072]
MC68HC908QY8VP MC68HC908QY8VP(a-trim)
MC68HC908QY8VPE MC68HC908QY8VPE(a-trim)
MC68HC908SR12CB@SDIP42 [DX0042] MC68HC908SR12CBE@SDIP42 [DX0042]
MC68HC908SR12CFA@TQFP48 [DX3007]
MC68HC908SR12CFAE@TQFP48 [DX3007]
MC68HC908SR12MB@SDIP42 [DX0042] MC68HC908SR12MBE@SDIP42 [DX0042]
MC68HC908SR12MFA@TQFP48 [DX3007]
MC68HC908SR12MFAE@TQFP48 [DX3007]
MC68HC908SR12VB@SDIP42 [DX0042] MC68HC908SR12VBE@SDIP42 [DX0042]
MC68HC908SR12VFA@TQFP48 [DX3007]
MC68HC908SR12VFAE@TQFP48 [DX3007]
MC68HCP11A0 [DX0001] MC68HCP11A0@PLCC52 [DX2052]
MC68HCP11A1 [DX0001] MC68HCP11A1@PLCC52 [DX2052]
MC68HCP11A8 [DX0001] MC68HCP11A8@PLCC52 [DX2052]
MC68HCP11E1@PLCC52 [DX2052] MC68HCP11E1@QFP52 [DX3010]
MC68HCP11E1CFU2 [DX3044] MC68HCP11E1CFU3 [DX3044]
MC68HCP11E1MFU2 [DX3044] MC68HCP11E1VFU2 [DX3044]
MC68HLC705J1ACDW [DX1033] MC68HLC705J1ACP [DX0001]
MC68HLC705J1ACS [DX1001] MC68HLC705J1ADW [DX1033]
MC68HLC705J1AP [DX0001] MC68HLC705J1AS [DX1001]
MC68HLC705KJ1CDW [DX1033] MC68HLC705KJ1CP [DX0001]
MC68HLC705KJ1CS [DX1001] MC68HLC705KJ1DW [DX1033]
MC68HLC705KJ1P [DX0001] MC68HLC705KJ1S [DX1001]
MC68HLC908JK1EIDW@SOIC20 [DX1033]
MC68HLC908JK1EIDWE@SOIC20 [DX1033]
MC68HLC908JK1EIP MC68HLC908JK1EIPE
MC68HLC908JK3EIDW@SOIC20 [DX1033]
MC68HLC908JK3EIDWE@SOIC20 [DX1033]
MC68HLC908JK3EIP MC68HLC908JK3EIPE
MC68HLC908JL3EIDW@SOIC28 [DX1033]
MC68HLC908JL3EIDWE@SOIC28 [DX1033]
MC68HLC908JL3EIFA@TQFP48 [DX3007]
MC68HLC908JL3EIFAE@TQFP48 [DX3007]
MC68HLC908JL3EIP MC68HLC908JL3EIPE
MC68HRC705J1ACDW [DX1033] MC68HRC705J1ACP [DX0001]
MC68HRC705J1ACS [DX1001] MC68HRC705J1ADW [DX1033]
MC68HRC705J1AP [DX0001] MC68HRC705J1AS [DX1001]
MC68HRC705KJ1CDW [DX1033] MC68HRC705KJ1CP [DX0001]
MC68HRC705KJ1CS [DX1001] MC68HRC705KJ1DW [DX1033]
MC68HRC705KJ1P [DX0001] MC68HRC705KJ1S [DX1001]
MC68HRC908JK1CDW@SOIC20 [DX1033]
MC68HRC908JK1CDWE@SOIC20 [DX1033]
MC68HRC908JK1CP MC68HRC908JK1CPE
MC68HRC908JK1ECDW@SOIC20 [DX1033]
MC68HRC908JK1ECDWE@SOIC20 [DX1033]
MC68HRC908JK1ECP MC68HRC908JK1ECPE
MC68HRC908JK1EMDW@SOIC20 [DX1033]

MC68HRC908JK1EMDWE@SOIC20 [DX1033]
MC68HRC908JK1EMP MC68HRC908JK1EMPE
MC68HRC908JK1EVDW@SOIC20 [DX1033]
MC68HRC908JK1EVDWE@SOIC20 [DX1033]
MC68HRC908JK1EVP MC68HRC908JK1EVPE
MC68HRC908JK1MDW@SOIC20 [DX1033]
MC68HRC908JK1MDWE@SOIC20 [DX1033]
MC68HRC908JK1MP MC68HRC908JK1MPE
MC68HRC908JK1VDW@SOIC20 [DX1033]
MC68HRC908JK1VDWE@SOIC20 [DX1033]
MC68HRC908JK1VP MC68HRC908JK1VPE
MC68HRC908JK3CDW@SOIC20 [DX1033]
MC68HRC908JK3CDWE@SOIC20 [DX1033]
MC68HRC908JK3CP MC68HRC908JK3CPE
MC68HRC908JK3ECDW@SOIC20 [DX1033]
MC68HRC908JK3ECDWE@SOIC20 [DX1033]
MC68HRC908JK3ECP MC68HRC908JK3ECPE
MC68HRC908JK3EMDW@SOIC20 [DX1033]
MC68HRC908JK3EMDWE@SOIC20 [DX1033]
MC68HRC908JK3EMP MC68HRC908JK3EMPE
MC68HRC908JK3EVDW@SOIC20 [DX1033]
MC68HRC908JK3EVDWE@SOIC20 [DX1033]
MC68HRC908JK3EVP MC68HRC908JK3EVPE
MC68HRC908JK3MDW@SOIC20 [DX1033]
MC68HRC908JK3MDWE@SOIC20 [DX1033]
MC68HRC908JK3MP MC68HRC908JK3MPE
MC68HRC908JK3VDW@SOIC20 [DX1033]
MC68HRC908JK3VDWE@SOIC20 [DX1033]
MC68HRC908JK3VP MC68HRC908JK3VPE
MC68HRC908JL3CDW@SOIC28 [DX1033]
MC68HRC908JL3CDWE@SOIC28 [DX1033]
MC68HRC908JL3CP MC68HRC908JL3CPE
MC68HRC908JL3ECDW@SOIC28 [DX1033]
MC68HRC908JL3ECDWE@SOIC28 [DX1033]
MC68HRC908JL3ECFA@TQFP48 [DX3007]
MC68HRC908JL3ECFAE@TQFP48 [DX3007]
MC68HRC908JL3ECP MC68HRC908JL3ECPE
MC68HRC908JL3EMDW@SOIC28 [DX1033]
MC68HRC908JL3EMDWE@SOIC28 [DX1033]
MC68HRC908JL3EMFA@TQFP48 [DX3007]
MC68HRC908JL3EMFAE@TQFP48 [DX3007]
MC68HRC908JL3EMP MC68HRC908JL3EMPE
MC68HRC908JL3EVDW@SOIC28 [DX1033]
MC68HRC908JL3EVDWE@SOIC28 [DX1033]
MC68HRC908JL3EVFA@TQFP48 [DX3007]
MC68HRC908JL3EVFAE@TQFP48 [DX3007]
MC68HRC908JL3EVP MC68HRC908JL3EVPE
MC68HRC908JL3MDW@SOIC28 [DX1033]

MC68HRC908JL3MDWE@SOIC28 [DX1033]
MC68HRC908JL3MP
MC68HRC908JL3MPE
MC68HRC908JL3VDW@SOIC28 [DX1033]
MC68HRC908JL3VDWE@SOIC28 [DX1033]
MC68HRC908JL3VP
MC68HRC908JL3VPE
MC68HSC705C8A [DX0001]
MC68HSC705C8A@PLCC44 [DX2044]
MC68HSC705C8A@SDIP42 [DX0042]
MC68HSC705C8A@TQFP44 [DX3002]
MC68HSC705J1ACDW [DX1033]
MC68HSC705J1ACP [DX0001]
MC68HSC705J1ACS [DX1001]
MC68HSC705J1ADW [DX1033]
MC68HSC705J1AP [DX0001]
MC68HSC705J1AS [DX1001]
MC68HSC705KJ1CDW [DX1033]
MC68HSC705KJ1CP [DX0001]
MC68HSC705KJ1CS [DX1001]
MC68HSC705KJ1DW [DX1033]
MC68HSC705KJ1P [DX0001]
MC68HSC705KJ1S [DX1001]
MC68HSR705J1ACDW [DX1033]
MC68HSR705J1ACP [DX0001]
MC68HSR705J1ACS [DX1001]
MC68HSR705J1ADW [DX1033]
MC68HSR705J1AP [DX0001]
MC68HSR705J1AS [DX1001]
MC68HSR705KJ1CDW [DX1033]
MC68HSR705KJ1CP [DX0001]
MC68HSR705KJ1CS [DX1001]
MC68HSR705KJ1DW [DX1033]
MC68HSR705KJ1P [DX0001]
MC68HSR705KJ1S [DX1001]
MC68S711E9@PLCC52 [DX2052]
MC68S711E9FN@PLCC52 [DX2052]
MC912B32ACFU8@TQFP80 [DX3018]
MC912B32AMFU8@TQFP80 [DX3018]
MC912B32AVFU8@TQFP80 [DX3018]
MC912BC32ACFU8@TQFP80 [DX3018]
MC912BC32AMFU8@TQFP80 [DX3018]
MC912BC32AVFU8@TQFP80 [DX3018]
MC912D60ACFU8@TQFP80 [DX3018]
MC912D60ACPV8@TQFP112 [DX3026]
MC912D60AMFU8@TQFP80 [DX3018]
MC912D60AMPV8@TQFP112 [DX3026]
MC912D60AVFU8@TQFP80 [DX3018]
MC912D60AVPV8@TQFP112 [DX3026]
MC912D60CCFU8@TQFP80 [DX3018]
MC912D60CCPV8@TQFP112 [DX3026]
MC912D60CMFU8@TQFP80 [DX3018]
MC912D60CMPV8@TQFP112 [DX3026]
MC912D60CVFU8@TQFP80 [DX3018]
MC912D60CVPV8@TQFP112 [DX3026]
MC912D60PCFU8@TQFP80 [DX3018]
MC912D60PCPV8@TQFP112 [DX3026]
MC912D60PMFU8@TQFP80 [DX3018]
MC912D60PMPV8@TQFP112 [DX3026]
MC912D60PVFU8@TQFP80 [DX3018]
MC912D60PVPV8@TQFP112 [DX3026]
MC912DG128ACPV@TQFP112 [DX3026]
MC912DG128AMPV@TQFP112 [DX3026]
MC912DG128AVPV@TQFP112 [DX3026]
MC912DG128CCPV@TQFP112 [DX3026]
MC912DG128CMPV@TQFP112 [DX3026]
MC912DG128CVPV@TQFP112 [DX3026]
MC912DG128PCPV@TQFP112 [DX3026]
MC912DG128PMPV@TQFP112 [DX3026]
MC912DG128PVPV@TQFP112 [DX3026]
MC912DT128ACPV@TQFP112 [DX3026]
MC912DT128AMPV@TQFP112 [DX3026]
MC912DT128AVPV@TQFP112 [DX3026]
MC912DT128CCPV@TQFP112 [DX3026]
MC912DT128CMPV@TQFP112 [DX3026]
MC912DT128CVPV@TQFP112 [DX3026]
MC912DT128PCPV@TQFP112 [DX3026]
MC912DT128PMPV@TQFP112 [DX3026]
MC912DT128PVPV@TQFP112 [DX3026]
MC9RS08KA1CDB@DFN6 [DX4000]
MC9RS08KA1CDB@DFN6(auto trim) [DX4000]
MC9RS08KA1CDBE@DFN6 [DX4000]
MC9RS08KA1CDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1CPC
MC9RS08KA1CPC(auto trim)
MC9RS08KA1CPCE
MC9RS08KA1CPCE(auto trim)
MC9RS08KA1CSC@SOIC8 [DX1030]

MC9RS08KA1CSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1CSCE@SOIC8 [DX1030]
MC9RS08KA1CSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA1MDB@DFN6 [DX4000]
MC9RS08KA1MDB@DFN6(auto trim) [DX4000]
MC9RS08KA1MDBE@DFN6 [DX4000]
MC9RS08KA1MDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1MPC MC9RS08KA1MPC(auto trim)
MC9RS08KA1MPCE MC9RS08KA1MPCE(auto trim)
MC9RS08KA1MSC@SOIC8 [DX1030]
MC9RS08KA1MSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1MSCE@SOIC8 [DX1030]
MC9RS08KA1MSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA1VDB@DFN6 [DX4000]
MC9RS08KA1VDB@DFN6(auto trim) [DX4000]
MC9RS08KA1VDBE@DFN6 [DX4000]
MC9RS08KA1VDBE@DFN6(auto trim) [DX4000]
MC9RS08KA1VPC MC9RS08KA1VPC(auto trim)
MC9RS08KA1VPCE MC9RS08KA1VPCE(auto trim)
MC9RS08KA1VSC@SOIC8 [DX1030]
MC9RS08KA1VSC@SOIC8(auto trim) [DX1030]
MC9RS08KA1VSCE@SOIC8 [DX1030]
MC9RS08KA1VSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2CDB@DFN6 [DX4000]
MC9RS08KA2CDB@DFN6(auto trim) [DX4000]
MC9RS08KA2CDBE@DFN6 [DX4000]
MC9RS08KA2CDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2CPC MC9RS08KA2CPC(auto trim)
MC9RS08KA2CPCE MC9RS08KA2CPCE(auto trim)
MC9RS08KA2CSC@SOIC8 [DX1030]
MC9RS08KA2CSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2CSCE@SOIC8 [DX1030]
MC9RS08KA2CSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2MDB@DFN6 [DX4000]
MC9RS08KA2MDB@DFN6(auto trim) [DX4000]
MC9RS08KA2MDBE@DFN6 [DX4000]
MC9RS08KA2MDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2MPC MC9RS08KA2MPC(auto trim)
MC9RS08KA2MPCE MC9RS08KA2MPCE(auto trim)
MC9RS08KA2MSC@SOIC8 [DX1030]
MC9RS08KA2MSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2MSCE@SOIC8 [DX1030]
MC9RS08KA2MSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA2VDB@DFN6 [DX4000]
MC9RS08KA2VDB@DFN6(auto trim) [DX4000]
MC9RS08KA2VDBE@DFN6 [DX4000]
MC9RS08KA2VDBE@DFN6(auto trim) [DX4000]
MC9RS08KA2VPC MC9RS08KA2VPC(auto trim)

MC9RS08KA2VPCE MC9RS08KA2VPCE(auto trim)
MC9RS08KA2VSC@SOIC8 [DX1030]
MC9RS08KA2VSC@SOIC8(auto trim) [DX1030]
MC9RS08KA2VSCE@SOIC8 [DX1030]
MC9RS08KA2VSCE@SOIC8(auto trim) [DX1030]
MC9RS08KA4CPG MC9RS08KA4CPG(auto trim)
MC9RS08KA4CPGE MC9RS08KA4CPGE(auto trim)
MC9RS08KA4CPJ MC9RS08KA4CPJ(auto trim)
MC9RS08KA4CPJE MC9RS08KA4CPJE(auto trim)
MC9RS08KA4CTG@TSSOP16 [DX1001]
MC9RS08KA4CTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4CTGE@TSSOP16 [DX1001]
MC9RS08KA4CTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA4CWG@SOIC16 [DX1033]
MC9RS08KA4CWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4CWGE@SOIC16 [DX1033]
MC9RS08KA4CWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4CWJ@SOIC20 [DX1033]
MC9RS08KA4CWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4CWJE@SOIC20 [DX1033]
MC9RS08KA4CWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA4MPG MC9RS08KA4MPG(auto trim)
MC9RS08KA4MPGE MC9RS08KA4MPGE(auto trim)
MC9RS08KA4MPJ MC9RS08KA4MPJ(auto trim)
MC9RS08KA4MPJE MC9RS08KA4MPJE(auto trim)
MC9RS08KA4MTG@TSSOP16 [DX1001]
MC9RS08KA4MTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4MTGE@TSSOP16 [DX1001]
MC9RS08KA4MTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA4MWG@SOIC16 [DX1033]
MC9RS08KA4MWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4MWGE@SOIC16 [DX1033]
MC9RS08KA4MWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4MWJ@SOIC20 [DX1033]
MC9RS08KA4MWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4MWJE@SOIC20 [DX1033]
MC9RS08KA4MWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA4VPG MC9RS08KA4VPG(auto trim)
MC9RS08KA4VPGE MC9RS08KA4VPGE(auto trim)
MC9RS08KA4VPJ MC9RS08KA4VPJ(auto trim)
MC9RS08KA4VPJE MC9RS08KA4VPJE(auto trim)
MC9RS08KA4VTG@TSSOP16 [DX1001]
MC9RS08KA4VTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA4VTGE@TSSOP16 [DX1001]
MC9RS08KA4VTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA4VWG@SOIC16 [DX1033]
MC9RS08KA4VWG@SOIC16(auto trim) [DX1033]
MC9RS08KA4VWGE@SOIC16 [DX1033]

MC9RS08KA4VWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA4VWJ@SOIC20 [DX1033]
MC9RS08KA4VWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA4VWJE@SOIC20 [DX1033]
MC9RS08KA4VWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8CPG MC9RS08KA8CPG(auto trim)
MC9RS08KA8CPGE MC9RS08KA8CPGE(auto trim)
MC9RS08KA8CPJ MC9RS08KA8CPJ(auto trim)
MC9RS08KA8CPJE MC9RS08KA8CPJE(auto trim)
MC9RS08KA8CTG@TSSOP16 [DX1001]
MC9RS08KA8CTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8CTGE@TSSOP16 [DX1001]
MC9RS08KA8CTGE@TSSOP16(auto trim [DX1001]
MC9RS08KA8CWG@SOIC16 [DX1033]
MC9RS08KA8CWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8CWGE@SOIC16 [DX1033]
MC9RS08KA8CWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8CWJ@SOIC20 [DX1033]
MC9RS08KA8CWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8CWJE@SOIC20 [DX1033]
MC9RS08KA8CWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8MPG MC9RS08KA8MPG(auto trim)
MC9RS08KA8MPGE MC9RS08KA8MPGE(auto trim)
MC9RS08KA8MPJ MC9RS08KA8MPJ(auto trim)
MC9RS08KA8MPJE MC9RS08KA8MPJE(auto trim)
MC9RS08KA8MTG@TSSOP16 [DX1001]
MC9RS08KA8MTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8MTGE@TSSOP16 [DX1001]
MC9RS08KA8MTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA8MWG@SOIC16 [DX1033]
MC9RS08KA8MWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8MWGE@SOIC16 [DX1033]
MC9RS08KA8MWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8MWJ@SOIC20 [DX1033]
MC9RS08KA8MWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8MWJE@SOIC20 [DX1033]
MC9RS08KA8MWJE@SOIC20(auto trim) [DX1033]
MC9RS08KA8VPG MC9RS08KA8VPG(auto trim)
MC9RS08KA8VPGE MC9RS08KA8VPGE(auto trim)
MC9RS08KA8VPJ MC9RS08KA8VPJ(auto trim)
MC9RS08KA8VPJE MC9RS08KA8VPJE(auto trim)
MC9RS08KA8VTG@TSSOP16 [DX1001]
MC9RS08KA8VTG@TSSOP16(auto trim) [DX1001]
MC9RS08KA8VTGE@TSSOP16 [DX1001]
MC9RS08KA8VTGE@TSSOP16(a trim) [DX1001]
MC9RS08KA8VWG@SOIC16 [DX1033]
MC9RS08KA8VWG@SOIC16(auto trim) [DX1033]
MC9RS08KA8VWGE@SOIC16 [DX1033]

MC9RS08KA8VWGE@SOIC16(auto trim) [DX1033]
MC9RS08KA8VWJ@SOIC20 [DX1033]
MC9RS08KA8VWJ@SOIC20(auto trim) [DX1033]
MC9RS08KA8VWJE@SOIC20 [DX1033]
MC9RS08KA8VWJE@SOIC20(auto trim) [DX1033]
MC9RS08KB12CDC@DFN8 [DX4004]
MC9RS08KB12CSC@SOIC8 [DX1030]
MC9RS08KB12CSG@SOIC16 [DX1030]
MC9RS08KB12CTG@TSSOP16 [DX1001]
MC9RS08KB12CWJ@SOIC20 [DX1033]
MC9RS08KB12MDC@DFN8 [DX4004]
MC9RS08KB12MSC@SOIC8 [DX1030]
MC9RS08KB12MSG@SOIC16 [DX1030]
MC9RS08KB12MTG@TSSOP16 [DX1001]
MC9RS08KB12MWJ@SOIC20 [DX1033]
MC9RS08KB12VDC@DFN8 [DX4004]
MC9RS08KB12VSC@SOIC8 [DX1030]
MC9RS08KB12VSG@SOIC16 [DX1030]
MC9RS08KB12VTG@TSSOP16 [DX1001]
MC9RS08KB12VWJ@SOIC20 [DX1033]
MC9RS08KB2CDC@DFN8 [DX4004]
MC9RS08KB2CSC@SOIC8 [DX1030]
MC9RS08KB2CSG@SOIC16 [DX1030]
MC9RS08KB2CTG@TSSOP16 [DX1001]
MC9RS08KB2CWJ@SOIC20 [DX1033]
MC9RS08KB2MDC@DFN8 [DX4004]
MC9RS08KB2MSC@SOIC8 [DX1030]
MC9RS08KB2MSG@SOIC16 [DX1030]
MC9RS08KB2MTG@TSSOP16 [DX1001]
MC9RS08KB2MWJ@SOIC20 [DX1033]
MC9RS08KB2VDC@DFN8 [DX4004]
MC9RS08KB2VSC@SOIC8 [DX1030]
MC9RS08KB2VSG@SOIC16 [DX1030]
MC9RS08KB2VTG@TSSOP16 [DX1001]
MC9RS08KB2VWJ@SOIC20 [DX1033]
MC9RS08KB4CDC@DFN8 [DX4004]
MC9RS08KB4CSC@SOIC8 [DX1030]
MC9RS08KB4CSG@SOIC16 [DX1030]
MC9RS08KB4CTG@TSSOP16 [DX1001]
MC9RS08KB4CWJ@SOIC20 [DX1033]
MC9RS08KB4MDC@DFN8 [DX4004]
MC9RS08KB4MSC@SOIC8 [DX1030]
MC9RS08KB4MSG@SOIC16 [DX1030]
MC9RS08KB4MTG@TSSOP16 [DX1001]
MC9RS08KB4MWJ@SOIC20 [DX1033]
MC9RS08KB4VDC@DFN8 [DX4004]
MC9RS08KB4VSC@SOIC8 [DX1030]
MC9RS08KB4VSG@SOIC16 [DX1030]
MC9RS08KB4VTG@TSSOP16 [DX1001]
MC9RS08KB4VWJ@SOIC20 [DX1033]
MC9RS08KB8CDC@DFN8 [DX4004]
MC9RS08KB8CSC@SOIC8 [DX1030]
MC9RS08KB8CSG@SOIC16 [DX1030]
MC9RS08KB8CTG@TSSOP16 [DX1001]
MC9RS08KB8CWJ@SOIC20 [DX1033]
MC9RS08KB8MDC@DFN8 [DX4004]
MC9RS08KB8MSC@SOIC8 [DX1030]
MC9RS08KB8MSG@SOIC16 [DX1030]
MC9RS08KB8MTG@TSSOP16 [DX1001]
MC9RS08KB8MWJ@SOIC20 [DX1033]
MC9RS08KB8VDC@DFN8 [DX4004]
MC9RS08KB8VSC@SOIC8 [DX1030]
MC9RS08KB8VSG@SOIC16 [DX1030]
MC9RS08KB8VTG@TSSOP16 [DX1001]
MC9RS08KB8VWJ@SOIC20 [DX1033]
MC9RS08LA8CFT@QFN48 [DX4021]
MC9RS08LA8CFTE@QFN48 [DX4021]
MC9RS08LA8CLF@QFP48 [DX3007]
MC9RS08LA8CLFE@QFP48 [DX3007]
MC9RS08LA8MFT@QFN48 [DX4021]
MC9RS08LA8MFTE@QFN48 [DX4021]
MC9RS08LA8MLF@QFP48 [DX3007]
MC9RS08LA8MLFE@QFP48 [DX3007]
MC9RS08LA8VFT@QFN48 [DX4021]
MC9RS08LA8VFTE@QFN48 [DX4021]
MC9RS08LA8VLF@QFP48 [DX3007]
MC9RS08LA8VLFE@QFP48 [DX3007]
MC9RS08LE4CWL@SOIC28 [DX1033]
MC9RS08LE4CWLE@SOIC28 [DX1033]
MC9RS08LE4MWL@SOIC28 [DX1033]
MC9RS08LE4MWLE@SOIC28 [DX1033]
MC9RS08LE4VWL@SOIC28 [DX1033]
MC9RS08LE4VWLE@SOIC28 [DX1033]
MC9S08AC128CFG@QFP44 [DX3003]
MC9S08AC128CFGE@QFP44 [DX3003]
MC9S08AC128CFU@QFP64 [DX3014]
MC9S08AC128CFUE@QFP64 [DX3014]
MC9S08AC128CLK@QFP80 [DX3017]
MC9S08AC128CLKE@QFP80 [DX3017]
MC9S08AC128MFG@QFP44 [DX3003]
MC9S08AC128MFGE@QFP44 [DX3003]

MC9S08AC128MFU@QFP64 [DX3014]　　MC9S08AC128MFUE@QFP64 [DX3014]
MC9S08AC128MLK@QFP80 [DX3017]　　MC9S08AC128MLKE@QFP80 [DX3017]
MC9S08AC128VFG@QFP44 [DX3003]　　MC9S08AC128VFGE@QFP44 [DX3003]
MC9S08AC128VFU@QFP64 [DX3014]　　MC9S08AC128VFUE@QFP64 [DX3014]
MC9S08AC128VLK@QFP80 [DX3017]　　MC9S08AC128VLKE@QFP80 [DX3017]
MC9S08AC16CFD@QFN48 [DX4021]　　MC9S08AC16CFDE@QFN48 [DX4021]
MC9S08AC16CFG@LQFP44 [DX3003]
MC9S08AC16CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16CFGE@LQFP44 [DX3003]
MC9S08AC16CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC16CFJ@QFP32 [DX3001]　　MC9S08AC16CFJE@QFP32 [DX3001]
MC9S08AC16MFD@QFN48 [DX4021]　　MC9S08AC16MFDE@QFN48 [DX4021]
MC9S08AC16MFG@LQFP44 [DX3003]
MC9S08AC16MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16MFGE@LQFP44 [DX3003]
MC9S08AC16MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC16MFJ@QFP32 [DX3001]　　MC9S08AC16MFJE@QFP32 [DX3001]
MC9S08AC16VFD@QFN48 [DX4021]　　MC9S08AC16VFDE@QFN48 [DX4021]
MC9S08AC16VFG@LQFP44 [DX3003]
MC9S08AC16VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC16VFGE@LQFP44 [DX3003]
MC9S08AC16VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC16VFJ@QFP32 [DX3001]　　MC9S08AC16VFJE@QFP32 [DX3001]
MC9S08AC32CFD@QFN48 [DX4021]　　MC9S08AC32CFDE@QFN48 [DX4021]
MC9S08AC32CFG@LQFP44 [DX3003]
MC9S08AC32CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32CFGE@LQFP44 [DX3003]
MC9S08AC32CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32CFJ@QFP32 [DX3001]　　MC9S08AC32CFJE@QFP32 [DX3001]
MC9S08AC32CFU@LQFP64 [DX3014]　　MC9S08AC32CFUE@LQFP64 [DX3014]
MC9S08AC32CPU@QFP64 [DX3011]　　MC9S08AC32CPUE@QFP64 [DX3011]
MC9S08AC32MFD@QFN48 [DX4021]　　MC9S08AC32MFDE@QFN48 [DX4021]
MC9S08AC32MFG@LQFP44 [DX3003]
MC9S08AC32MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32MFGE@LQFP44 [DX3003]
MC9S08AC32MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32MFJ@QFP32 [DX3001]　　MC9S08AC32MFJE@QFP32 [DX3001]
MC9S08AC32MFU@LQFP64 [DX3014]　　MC9S08AC32MFUE@LQFP64 [DX3014]
MC9S08AC32MPU@QFP64 [DX3011]　　MC9S08AC32MPUE@QFP64 [DX3011]
MC9S08AC32VFD@QFN48 [DX4021]　　MC9S08AC32VFDE@QFN48 [DX4021]
MC9S08AC32VFG@LQFP44 [DX3003]
MC9S08AC32VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC32VFGE@LQFP44 [DX3003]
MC9S08AC32VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC32VFJ@QFP32 [DX3001]　　MC9S08AC32VFJE@QFP32 [DX3001]
MC9S08AC32VFU@LQFP64 [DX3014]　　MC9S08AC32VFUE@LQFP64 [DX3014]
MC9S08AC32VPU@QFP64 [DX3011]　　MC9S08AC32VPUE@QFP64 [DX3011]
MC9S08AC48CFD@QFN48 [DX4021]　　MC9S08AC48CFDE@QFN48 [DX4021]

MC9S08AC48CFG@LQFP44 [DX3003]
MC9S08AC48CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48CFGE@LQFP44 [DX3003]
MC9S08AC48CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48CFJ@QFP32 [DX3001]　　MC9S08AC48CFJE@QFP32 [DX3001]
MC9S08AC48CFU@LQFP64 [DX3014]　　MC9S08AC48CFUE@LQFP64 [DX3014]
MC9S08AC48CPU@QFP64 [DX3011]　　MC9S08AC48CPUE@QFP64 [DX3011]
MC9S08AC48MFD@QFN48 [DX4021]　　MC9S08AC48MFDE@QFN48 [DX4021]
MC9S08AC48MFG@LQFP44 [DX3003]
MC9S08AC48MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48MFGE@LQFP44 [DX3003]
MC9S08AC48MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48MFJ@QFP32 [DX3001]　　MC9S08AC48MFJE@QFP32 [DX3001]
MC9S08AC48MFU@LQFP64 [DX3014]　　MC9S08AC48MFUE@LQFP64 [DX3014]
MC9S08AC48MPU@QFP64 [DX3011]　　MC9S08AC48MPUE@QFP64 [DX3011]
MC9S08AC48VFD@QFN48 [DX4021]　　MC9S08AC48VFDE@QFN48 [DX4021]
MC9S08AC48VFG@LQFP44 [DX3003]
MC9S08AC48VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC48VFGE@LQFP44 [DX3003]
MC9S08AC48VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC48VFJ@QFP32 [DX3001]　　MC9S08AC48VFJE@QFP32 [DX3001]
MC9S08AC48VFU@LQFP64 [DX3014]　　MC9S08AC48VFUE@LQFP64 [DX3014]
MC9S08AC48VPU@QFP64 [DX3011]　　MC9S08AC48VPUE@QFP64 [DX3011]
MC9S08AC60CFD@QFN48 [DX4021]　　MC9S08AC60CFDE@QFN48 [DX4021]
MC9S08AC60CFG@LQFP44 [DX3003]
MC9S08AC60CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60CFGE@LQFP44 [DX3003]
MC9S08AC60CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60CFJ@QFP32 [DX3001]　　MC9S08AC60CFJE@QFP32 [DX3001]
MC9S08AC60CFU@LQFP64 [DX3014]　　MC9S08AC60CFUE@LQFP64 [DX3014]
MC9S08AC60CPU@QFP64 [DX3011]　　MC9S08AC60CPUE@QFP64 [DX3011]
MC9S08AC60MFD@QFN48 [DX4021]　　MC9S08AC60MFDE@QFN48 [DX4021]
MC9S08AC60MFG@LQFP44 [DX3003]
MC9S08AC60MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60MFGE@LQFP44 [DX3003]
MC9S08AC60MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60MFJ@QFP32 [DX3001]　　MC9S08AC60MFJE@QFP32 [DX3001]
MC9S08AC60MFU@LQFP64 [DX3014]　　MC9S08AC60MFUE@LQFP64 [DX3014]
MC9S08AC60MPU@QFP64 [DX3011]　　MC9S08AC60MPUE@QFP64 [DX3011]
MC9S08AC60VFD@QFN48 [DX4021]　　MC9S08AC60VFDE@QFN48 [DX4021]
MC9S08AC60VFG@LQFP44 [DX3003]
MC9S08AC60VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC60VFGE@LQFP44 [DX3003]
MC9S08AC60VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC60VFJ@QFP32 [DX3001]　　MC9S08AC60VFJE@QFP32 [DX3001]
MC9S08AC60VFU@LQFP64 [DX3014]　　MC9S08AC60VFUE@LQFP64 [DX3014]
MC9S08AC60VPU@QFP64 [DX3011]　　MC9S08AC60VPUE@QFP64 [DX3011]
MC9S08AC8CFD@QFN48 [DX4021]　　MC9S08AC8CFDE@QFN48 [DX4021]

MC9S08AC8CFG@LQFP44 [DX3003]
MC9S08AC8CFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8CFGE@LQFP44 [DX3003]
MC9S08AC8CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC8CFJ@QFP32 [DX3001]
MC9S08AC8CFJE@QFP32 [DX3001]
MC9S08AC8MFD@QFN48 [DX4021]
MC9S08AC8MFDE@QFN48 [DX4021]
MC9S08AC8MFG@LQFP44 [DX3003]
MC9S08AC8MFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8MFGE@LQFP44 [DX3003]
MC9S08AC8MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC8MFJ@QFP32 [DX3001]
MC9S08AC8MFJE@QFP32 [DX3001]
MC9S08AC8VFD@QFN48 [DX4021]
MC9S08AC8VFDE@QFN48 [DX4021]
MC9S08AC8VFG@LQFP44 [DX3003]
MC9S08AC8VFG@LQFP44(*) [SA245A+B4404]
MC9S08AC8VFGE@LQFP44 [DX3003]
MC9S08AC8VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AC8VFJ@QFP32 [DX3001]
MC9S08AC8VFJE@QFP32 [DX3001]
MC9S08AC96CFG@QFP44 [DX3003]
MC9S08AC96CFGE@QFP44 [DX3003]
MC9S08AC96CFU@QFP64 [DX3014]
MC9S08AC96CFUE@QFP64 [DX3014]
MC9S08AC96CLK@QFP80 [DX3017]
MC9S08AC96CLKE@QFP80 [DX3017]
MC9S08AC96MFG@QFP44 [DX3003]
MC9S08AC96MFGE@QFP44 [DX3003]
MC9S08AC96MFU@QFP64 [DX3014]
MC9S08AC96MFUE@QFP64 [DX3014]
MC9S08AC96MLK@QFP80 [DX3017]
MC9S08AC96MLKE@QFP80 [DX3017]
MC9S08AC96VFG@QFP44 [DX3003]
MC9S08AC96VFGE@QFP44 [DX3003]
MC9S08AC96VFU@QFP64 [DX3014]
MC9S08AC96VFUE@QFP64 [DX3014]
MC9S08AC96VLK@QFP80 [DX3017]
MC9S08AC96VLKE@QFP80 [DX3017]
MC9S08AW16CFD@QFN48 [DX4021]
MC9S08AW16CFDE@QFN48 [DX4021]
MC9S08AW16CFG@LQFP44 [DX3003]
MC9S08AW16CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16CFGE@LQFP44 [DX3003]
MC9S08AW16CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16CFU@LQFP64 [DX3014]
MC9S08AW16CFUE@LQFP64 [DX3014]
MC9S08AW16CPU@QFP64 [DX3011]
MC9S08AW16CPUE@QFP64 [DX3011]
MC9S08AW16MFD@QFN48 [DX4021]
MC9S08AW16MFDE@QFN48 [DX4021]
MC9S08AW16MFG@LQFP44 [DX3003]
MC9S08AW16MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16MFGE@LQFP44 [DX3003]
MC9S08AW16MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16MFU@LQFP64 [DX3014]
MC9S08AW16MFUE@LQFP64 [DX3014]
MC9S08AW16MPU@QFP64 [DX3011]
MC9S08AW16MPUE@QFP64 [DX3011]
MC9S08AW16VFD@QFN48 [DX4021]
MC9S08AW16VFDE@QFN48 [DX4021]
MC9S08AW16VFG@LQFP44 [DX3003]
MC9S08AW16VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW16VFGE@LQFP44 [DX3003]
MC9S08AW16VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW16VFU@LQFP64 [DX3014]
MC9S08AW16VFUE@LQFP64 [DX3014]
MC9S08AW16VPU@QFP64 [DX3011]
MC9S08AW16VPUE@QFP64 [DX3011]
MC9S08AW32CFD@QFN48 [DX4021]
MC9S08AW32CFDE@QFN48 [DX4021]

MC9S08AW32CFG@LQFP44 [DX3003]
MC9S08AW32CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW32CFGE@LQFP44 [DX3003]
MC9S08AW32CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32CFU@LQFP64 [DX3014]　　MC9S08AW32CFUE@LQFP64 [DX3014]
MC9S08AW32CPU@QFP64 [DX3011]　　MC9S08AW32CPUE@QFP64 [DX3011]
MC9S08AW32MFD@QFN48 [DX4021]　　MC9S08AW32MFDE@QFN48 [DX4021]
MC9S08AW32MFG@LQFP44 [DX3003]
MC9S08AW32MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW32MFGE@LQFP44 [DX3003]
MC9S08AW32MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32MFU@LQFP64 [DX3014]　　MC9S08AW32MFUE@LQFP64 [DX3014]
MC9S08AW32MPU@QFP64 [DX3011]　　MC9S08AW32MPUE@QFP64 [DX3011]
MC9S08AW32VFD@QFN48 [DX4021]　　MC9S08AW32VFDE@QFN48 [DX4021]
MC9S08AW32VFG@LQFP44 [DX3003]
MC9S08AW32VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW32VFGE@LQFP44 [DX3003]
MC9S08AW32VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW32VFU@LQFP64 [DX3014]　　MC9S08AW32VFUE@LQFP64 [DX3014]
MC9S08AW32VPU@QFP64 [DX3011]　　MC9S08AW32VPUE@QFP64 [DX3011]
MC9S08AW48CFD@QFN48 [DX4021]　　MC9S08AW48CFDE@QFN48 [DX4021]
MC9S08AW48CFG@LQFP44 [DX3003]
MC9S08AW48CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48CFGE@LQFP44 [DX3003]
MC9S08AW48CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48CFU@LQFP64 [DX3014]　　MC9S08AW48CFUE@LQFP64 [DX3014]
MC9S08AW48CPU@QFP64 [DX3011]　　MC9S08AW48CPUE@QFP64 [DX3011]
MC9S08AW48MFD@QFN48 [DX4021]　　MC9S08AW48MFDE@QFN48 [DX4021]
MC9S08AW48MFG@LQFP44 [DX3003]
MC9S08AW48MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48MFGE@LQFP44 [DX3003]
MC9S08AW48MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48MFU@LQFP64 [DX3014]　　MC9S08AW48MFUE@LQFP64 [DX3014]
MC9S08AW48MPU@QFP64 [DX3011]　　MC9S08AW48MPUE@QFP64 [DX3011]
MC9S08AW48VFD@QFN48 [DX4021]　　MC9S08AW48VFDE@QFN48 [DX4021]
MC9S08AW48VFG@LQFP44 [DX3003]
MC9S08AW48VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW48VFGE@LQFP44 [DX3003]
MC9S08AW48VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW48VFU@LQFP64 [DX3014]　　MC9S08AW48VFUE@LQFP64 [DX3014]
MC9S08AW48VPU@QFP64 [DX3011]　　MC9S08AW48VPUE@QFP64 [DX3011]
MC9S08AW60CFD@QFN48 [DX4021]　　MC9S08AW60CFDE@QFN48 [DX4021]
MC9S08AW60CFG@LQFP44 [DX3003]
MC9S08AW60CFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60CFGE@LQFP44 [DX3003]
MC9S08AW60CFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60CFU@LQFP64 [DX3014]　　MC9S08AW60CFUE@LQFP64 [DX3014]
MC9S08AW60CPU@QFP64 [DX3011]　　MC9S08AW60CPUE@QFP64 [DX3011]

MC9S08AW60MFD@QFN48 [DX4021]　　MC9S08AW60MFDE@QFN48 [DX4021]
MC9S08AW60MFG@LQFP44 [DX3003]
MC9S08AW60MFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60MFGE@LQFP44 [DX3003]
MC9S08AW60MFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60MFU@LQFP64 [DX3014]　　MC9S08AW60MFUE@LQFP64 [DX3014]
MC9S08AW60MPU@QFP64 [DX3011]　　MC9S08AW60MPUE@QFP64 [DX3011]
MC9S08AW60VFD@QFN48 [DX4021]　　MC9S08AW60VFDE@QFN48 [DX4021]
MC9S08AW60VFG@LQFP44 [DX3003]
MC9S08AW60VFG@LQFP44(*) [SA245A+B4404]
MC9S08AW60VFGE@LQFP44 [DX3003]
MC9S08AW60VFGE@LQFP44(*) [SA245A+B4404]
MC9S08AW60VFU@LQFP64 [DX3014]　　MC9S08AW60VFUE@LQFP64 [DX3014]
MC9S08AW60VPU@QFP64 [DX3011]　　MC9S08AW60VPUE@QFP64 [DX3011]
MC9S08DN16CLC@QFP32 [DX3001]　　MC9S08DN16CLCE@QFP32 [DX3001]
MC9S08DN16CLF@QFP48 [DX3007]　　MC9S08DN16CLFE@QFP48 [DX3007]
MC9S08DN16CLH@QFP64 [DX3011]　　MC9S08DN16CLHE@QFP64 [DX3011]
MC9S08DN16MLC@QFP32 [DX3001]　　MC9S08DN16MLCE@QFP32 [DX3001]
MC9S08DN16MLF@QFP48 [DX3007]　　MC9S08DN16MLFE@QFP48 [DX3007]
MC9S08DN16MLH@QFP64 [DX3011]　　MC9S08DN16MLHE@QFP64 [DX3011]
MC9S08DN16VLC@QFP32 [DX3001]　　MC9S08DN16VLCE@QFP32 [DX3001]
MC9S08DN16VLF@QFP48 [DX3007]　　MC9S08DN16VLFE@QFP48 [DX3007]
MC9S08DN16VLH@QFP64 [DX3011]　　MC9S08DN16VLHE@QFP64 [DX3011]
MC9S08DN32CLC@QFP32 [DX3001]　　MC9S08DN32CLCE@QFP32 [DX3001]
MC9S08DN32CLF@QFP48 [DX3007]　　MC9S08DN32CLFE@QFP48 [DX3007]
MC9S08DN32CLH@QFP64 [DX3011]　　MC9S08DN32CLHE@QFP64 [DX3011]
MC9S08DN32MLC@QFP32 [DX3001]　　MC9S08DN32MLCE@QFP32 [DX3001]
MC9S08DN32MLF@QFP48 [DX3007]　　MC9S08DN32MLFE@QFP48 [DX3007]
MC9S08DN32MLH@QFP64 [DX3011]　　MC9S08DN32MLHE@QFP64 [DX3011]
MC9S08DN32VLC@QFP32 [DX3001]　　MC9S08DN32VLCE@QFP32 [DX3001]
MC9S08DN32VLF@QFP48 [DX3007]　　MC9S08DN32VLFE@QFP48 [DX3007]
MC9S08DN32VLH@QFP64 [DX3011]　　MC9S08DN32VLHE@QFP64 [DX3011]
MC9S08DN48CLC@QFP32 [DX3001]　　MC9S08DN48CLCE@QFP32 [DX3001]
MC9S08DN48CLF@QFP48 [DX3007]　　MC9S08DN48CLFE@QFP48 [DX3007]
MC9S08DN48CLH@QFP64 [DX3011]　　MC9S08DN48CLHE@QFP64 [DX3011]
MC9S08DN48MLC@QFP32 [DX3001]　　MC9S08DN48MLCE@QFP32 [DX3001]
MC9S08DN48MLF@QFP48 [DX3007]　　MC9S08DN48MLFE@QFP48 [DX3007]
MC9S08DN48MLH@QFP64 [DX3011]　　MC9S08DN48MLHE@QFP64 [DX3011]
MC9S08DN48VLC@QFP32 [DX3001]　　MC9S08DN48VLCE@QFP32 [DX3001]
MC9S08DN48VLF@QFP48 [DX3007]　　MC9S08DN48VLFE@QFP48 [DX3007]
MC9S08DN48VLH@QFP64 [DX3011]　　MC9S08DN48VLHE@QFP64 [DX3011]
MC9S08DN60CLC@QFP32 [DX3001]　　MC9S08DN60CLCE@QFP32 [DX3001]
MC9S08DN60CLF@QFP48 [DX3007]　　MC9S08DN60CLFE@QFP48 [DX3007]
MC9S08DN60CLH@QFP64 [DX3011]　　MC9S08DN60CLHE@QFP64 [DX3011]
MC9S08DN60MLC@QFP32 [DX3001]　　MC9S08DN60MLCE@QFP32 [DX3001]
MC9S08DN60MLF@QFP48 [DX3007]　　MC9S08DN60MLFE@QFP48 [DX3007]
MC9S08DN60MLH@QFP64 [DX3011]　　MC9S08DN60MLHE@QFP64 [DX3011]
MC9S08DN60VLC@QFP32 [DX3001]　　MC9S08DN60VLCE@QFP32 [DX3001]

MC9S08DN60VLF@QFP48 [DX3007]
MC9S08DN60VLFE@QFP48 [DX3007]
MC9S08DN60VLH@QFP64 [DX3011]
MC9S08DN60VLHE@QFP64 [DX3011]
MC9S08DV128CLF@QFP48 [DX3007]
MC9S08DV128CLFE@QFP48 [DX3007]
MC9S08DV128CLH@QFP64 [DX3011]
MC9S08DV128CLHE@QFP64 [DX3011]
MC9S08DV128CLL@QFP100 [DX3021]
MC9S08DV128CLLE@QFP100 [DX3021]
MC9S08DV128MLF@QFP48 [DX3007]
MC9S08DV128MLFE@QFP48 [DX3007]
MC9S08DV128MLH@QFP64 [DX3011]
MC9S08DV128MLHE@QFP64 [DX3011]
MC9S08DV128MLL@QFP100 [DX3021]
MC9S08DV128MLLE@QFP100 [DX3021]
MC9S08DV128VLF@QFP48 [DX3007]
MC9S08DV128VLFE@QFP48 [DX3007]
MC9S08DV128VLH@QFP64 [DX3011]
MC9S08DV128VLHE@QFP64 [DX3011]
MC9S08DV128VLL@QFP100 [DX3021]
MC9S08DV128VLLE@QFP100 [DX3021]
MC9S08DV16CLC@QFP32 [DX3001]
MC9S08DV16CLCE@QFP32 [DX3001]
MC9S08DV16CLF@QFP48 [DX3007]
MC9S08DV16CLFE@QFP48 [DX3007]
MC9S08DV16CLH@QFP64 [DX3011]
MC9S08DV16CLHE@QFP64 [DX3011]
MC9S08DV16MLC@QFP32 [DX3001]
MC9S08DV16MLCE@QFP32 [DX3001]
MC9S08DV16MLF@QFP48 [DX3007]
MC9S08DV16MLFE@QFP48 [DX3007]
MC9S08DV16MLH@QFP64 [DX3011]
MC9S08DV16MLHE@QFP64 [DX3011]
MC9S08DV16VLC@QFP32 [DX3001]
MC9S08DV16VLCE@QFP32 [DX3001]
MC9S08DV16VLF@QFP48 [DX3007]
MC9S08DV16VLFE@QFP48 [DX3007]
MC9S08DV16VLH@QFP64 [DX3011]
MC9S08DV16VLHE@QFP64 [DX3011]
MC9S08DV32CLC@QFP32 [DX3001]
MC9S08DV32CLCE@QFP32 [DX3001]
MC9S08DV32CLF@QFP48 [DX3007]
MC9S08DV32CLFE@QFP48 [DX3007]
MC9S08DV32CLH@QFP64 [DX3011]
MC9S08DV32CLHE@QFP64 [DX3011]
MC9S08DV32MLC@QFP32 [DX3001]
MC9S08DV32MLCE@QFP32 [DX3001]
MC9S08DV32MLF@QFP48 [DX3007]
MC9S08DV32MLFE@QFP48 [DX3007]
MC9S08DV32MLH@QFP64 [DX3011]
MC9S08DV32MLHE@QFP64 [DX3011]
MC9S08DV32VLC@QFP32 [DX3001]
MC9S08DV32VLCE@QFP32 [DX3001]
MC9S08DV32VLF@QFP48 [DX3007]
MC9S08DV32VLFE@QFP48 [DX3007]
MC9S08DV32VLH@QFP64 [DX3011]
MC9S08DV32VLHE@QFP64 [DX3011]
MC9S08DV48CLC@QFP32 [DX3001]
MC9S08DV48CLCE@QFP32 [DX3001]
MC9S08DV48CLF@QFP48 [DX3007]
MC9S08DV48CLFE@QFP48 [DX3007]
MC9S08DV48CLH@QFP64 [DX3011]
MC9S08DV48CLHE@QFP64 [DX3011]
MC9S08DV48MLC@QFP32 [DX3001]
MC9S08DV48MLCE@QFP32 [DX3001]
MC9S08DV48MLF@QFP48 [DX3007]
MC9S08DV48MLFE@QFP48 [DX3007]
MC9S08DV48MLH@QFP64 [DX3011]
MC9S08DV48MLHE@QFP64 [DX3011]
MC9S08DV48VLC@QFP32 [DX3001]
MC9S08DV48VLCE@QFP32 [DX3001]
MC9S08DV48VLF@QFP48 [DX3007]
MC9S08DV48VLFE@QFP48 [DX3007]
MC9S08DV48VLH@QFP64 [DX3011]
MC9S08DV48VLHE@QFP64 [DX3011]
MC9S08DV60CLC@QFP32 [DX3001]
MC9S08DV60CLCE@QFP32 [DX3001]
MC9S08DV60CLF@QFP48 [DX3007]
MC9S08DV60CLFE@QFP48 [DX3007]
MC9S08DV60CLH@QFP64 [DX3011]
MC9S08DV60CLHE@QFP64 [DX3011]
MC9S08DV60MLC@QFP32 [DX3001]
MC9S08DV60MLCE@QFP32 [DX3001]
MC9S08DV60MLF@QFP48 [DX3007]
MC9S08DV60MLFE@QFP48 [DX3007]
MC9S08DV60MLH@QFP64 [DX3011]
MC9S08DV60MLHE@QFP64 [DX3011]
MC9S08DV60VLC@QFP32 [DX3001]
MC9S08DV60VLCE@QFP32 [DX3001]
MC9S08DV60VLF@QFP48 [DX3007]
MC9S08DV60VLFE@QFP48 [DX3007]
MC9S08DV60VLH@QFP64 [DX3011]
MC9S08DV60VLHE@QFP64 [DX3011]
MC9S08DV96CLF@QFP48 [DX3007]
MC9S08DV96CLFE@QFP48 [DX3007]

MC9S08DV96CLH@QFP64 [DX3011]
MC9S08DV96CLHE@QFP64 [DX3011]
MC9S08DV96CLL@QFP100 [DX3021]
MC9S08DV96CLLE@QFP100 [DX3021]
MC9S08DV96MLF@QFP48 [DX3007]
MC9S08DV96MLFE@QFP48 [DX3007]
MC9S08DV96MLH@QFP64 [DX3011]
MC9S08DV96MLHE@QFP64 [DX3011]
MC9S08DV96MLL@QFP100 [DX3021]
MC9S08DV96MLLE@QFP100 [DX3021]
MC9S08DV96VLF@QFP48 [DX3007]
MC9S08DV96VLFE@QFP48 [DX3007]
MC9S08DV96VLH@QFP64 [DX3011]
MC9S08DV96VLHE@QFP64 [DX3011]
MC9S08DV96VLL@QFP100 [DX3021]
MC9S08DV96VLLE@QFP100 [DX3021]
MC9S08DZ128CLF@QFP48 [DX3007]
MC9S08DZ128CLFE@QFP48 [DX3007]
MC9S08DZ128CLH@QFP64 [DX3011]
MC9S08DZ128CLHE@QFP64 [DX3011]
MC9S08DZ128CLL@QFP100 [DX3021]
MC9S08DZ128CLLE@QFP100 [DX3021]
MC9S08DZ128MLF@QFP48 [DX3007]
MC9S08DZ128MLFE@QFP48 [DX3007]
MC9S08DZ128MLH@QFP64 [DX3011]
MC9S08DZ128MLHE@QFP64 [DX3011]
MC9S08DZ128MLL@QFP100 [DX3021]
MC9S08DZ128MLLE@QFP100 [DX3021]
MC9S08DZ128VLF@QFP48 [DX3007]
MC9S08DZ128VLFE@QFP48 [DX3007]
MC9S08DZ128VLH@QFP64 [DX3011]
MC9S08DZ128VLHE@QFP64 [DX3011]
MC9S08DZ128VLL@QFP100 [DX3021]
MC9S08DZ128VLLE@QFP100 [DX3021]
MC9S08DZ16CLC@QFP32 [DX3001]
MC9S08DZ16CLCE@QFP32 [DX3001]
MC9S08DZ16CLF@QFP48 [DX3007]
MC9S08DZ16CLFE@QFP48 [DX3007]
MC9S08DZ16CLH@QFP64 [DX3011]
MC9S08DZ16CLHE@QFP64 [DX3011]
MC9S08DZ16MLC@QFP32 [DX3001]
MC9S08DZ16MLCE@QFP32 [DX3001]
MC9S08DZ16MLF@QFP48 [DX3007]
MC9S08DZ16MLFE@QFP48 [DX3007]
MC9S08DZ16MLH@QFP64 [DX3011]
MC9S08DZ16MLHE@QFP64 [DX3011]
MC9S08DZ16VLC@QFP32 [DX3001]
MC9S08DZ16VLCE@QFP32 [DX3001]
MC9S08DZ16VLF@QFP48 [DX3007]
MC9S08DZ16VLFE@QFP48 [DX3007]
MC9S08DZ16VLH@QFP64 [DX3011]
MC9S08DZ16VLHE@QFP64 [DX3011]
MC9S08DZ32CLC@QFP32 [DX3001]
MC9S08DZ32CLCE@QFP32 [DX3001]
MC9S08DZ32CLF@QFP48 [DX3007]
MC9S08DZ32CLFE@QFP48 [DX3007]
MC9S08DZ32CLH@QFP64 [DX3011]
MC9S08DZ32CLHE@QFP64 [DX3011]
MC9S08DZ32MLC@QFP32 [DX3001]
MC9S08DZ32MLCE@QFP32 [DX3001]
MC9S08DZ32MLF@QFP48 [DX3007]
MC9S08DZ32MLFE@QFP48 [DX3007]
MC9S08DZ32MLH@QFP64 [DX3011]
MC9S08DZ32MLHE@QFP64 [DX3011]
MC9S08DZ32VLC@QFP32 [DX3001]
MC9S08DZ32VLCE@QFP32 [DX3001]
MC9S08DZ32VLF@QFP48 [DX3007]
MC9S08DZ32VLFE@QFP48 [DX3007]
MC9S08DZ32VLH@QFP64 [DX3011]
MC9S08DZ32VLHE@QFP64 [DX3011]
MC9S08DZ48CLC@QFP32 [DX3001]
MC9S08DZ48CLCE@QFP32 [DX3001]
MC9S08DZ48CLF@QFP48 [DX3007]
MC9S08DZ48CLFE@QFP48 [DX3007]
MC9S08DZ48CLH@QFP64 [DX3011]
MC9S08DZ48CLHE@QFP64 [DX3011]
MC9S08DZ48MLC@QFP32 [DX3001]
MC9S08DZ48MLCE@QFP32 [DX3001]
MC9S08DZ48MLF@QFP48 [DX3007]
MC9S08DZ48MLFE@QFP48 [DX3007]
MC9S08DZ48MLH@QFP64 [DX3011]
MC9S08DZ48MLHE@QFP64 [DX3011]
MC9S08DZ48VLC@QFP32 [DX3001]
MC9S08DZ48VLCE@QFP32 [DX3001]
MC9S08DZ48VLF@QFP48 [DX3007]
MC9S08DZ48VLFE@QFP48 [DX3007]
MC9S08DZ48VLH@QFP64 [DX3011]
MC9S08DZ48VLHE@QFP64 [DX3011]
MC9S08DZ60CLC@QFP32 [DX3001]
MC9S08DZ60CLCE@QFP32 [DX3001]
MC9S08DZ60CLF@QFP48 [DX3007]
MC9S08DZ60CLFE@QFP48 [DX3007]
MC9S08DZ60CLH@QFP64 [DX3011]
MC9S08DZ60CLHE@QFP64 [DX3011]
MC9S08DZ60MLC@QFP32 [DX3001]
MC9S08DZ60MLCE@QFP32 [DX3001]

MC9S08DZ60MLF@QFP48 [DX3007]
MC9S08DZ60MLFE@QFP48 [DX3007]
MC9S08DZ60MLH@QFP64 [DX3011]
MC9S08DZ60MLHE@QFP64 [DX3011]
MC9S08DZ60VLC@QFP32 [DX3001]
MC9S08DZ60VLCE@QFP32 [DX3001]
MC9S08DZ60VLF@QFP48 [DX3007]
MC9S08DZ60VLFE@QFP48 [DX3007]
MC9S08DZ60VLH@QFP64 [DX3011]
MC9S08DZ60VLHE@QFP64 [DX3011]
MC9S08DZ96CLF@QFP48 [DX3007]
MC9S08DZ96CLFE@QFP48 [DX3007]
MC9S08DZ96CLH@QFP64 [DX3011]
MC9S08DZ96CLHE@QFP64 [DX3011]
MC9S08DZ96CLL@QFP100 [DX3021]
MC9S08DZ96CLLE@QFP100 [DX3021]
MC9S08DZ96MLF@QFP48 [DX3007]
MC9S08DZ96MLFE@QFP48 [DX3007]
MC9S08DZ96MLH@QFP64 [DX3011]
MC9S08DZ96MLHE@QFP64 [DX3011]
MC9S08DZ96MLL@QFP100 [DX3021]
MC9S08DZ96MLLE@QFP100 [DX3021]
MC9S08DZ96VLF@QFP48 [DX3007]
MC9S08DZ96VLFE@QFP48 [DX3007]
MC9S08DZ96VLH@QFP64 [DX3011]
MC9S08DZ96VLHE@QFP64 [DX3011]
MC9S08DZ96VLL@QFP100 [DX3021]
MC9S08DZ96VLLE@QFP100 [DX3021]
MC9S08EL16CTJ@TSSOP20 [DX1000]
MC9S08EL16CTJE@TSSOP20 [DX1000]
MC9S08EL16CTL@TSSOP28 [DX1001]
MC9S08EL16CTLE@TSSOP28 [DX1001]
MC9S08EL16MTJ@TSSOP20 [DX1000]
MC9S08EL16MTJE@TSSOP20 [DX1000]
MC9S08EL16MTL@TSSOP28 [DX1001]
MC9S08EL16MTLE@TSSOP28 [DX1001]
MC9S08EL16VTJ@TSSOP20 [DX1000]
MC9S08EL16VTJE@TSSOP20 [DX1000]
MC9S08EL16VTL@TSSOP28 [DX1001]
MC9S08EL16VTLE@TSSOP28 [DX1001]
MC9S08EL32CTJ@TSSOP20 [DX1000]
MC9S08EL32CTJE@TSSOP20 [DX1000]
MC9S08EL32CTL@TSSOP28 [DX1001]
MC9S08EL32CTLE@TSSOP28 [DX1001]
MC9S08EL32MTJ@TSSOP20 [DX1000]
MC9S08EL32MTJE@TSSOP20 [DX1000]
MC9S08EL32MTL@TSSOP28 [DX1001]
MC9S08EL32MTLE@TSSOP28 [DX1001]
MC9S08EL32VTJ@TSSOP20 [DX1000]
MC9S08EL32VTJE@TSSOP20 [DX1000]
MC9S08EL32VTL@TSSOP28 [DX1001]
MC9S08EL32VTLE@TSSOP28 [DX1001]
MC9S08FL16CBM@SDIP32 [DX0032]
MC9S08FL16CBM@SDIP32(auto trim) [DX0032]
MC9S08FL16CLC@LQFP32 [DX3001]
MC9S08FL16CLC@LQFP32(auto trim) [DX3001]
MC9S08FL16MBM@SDIP32 [DX0032]
MC9S08FL16MBM@SDIP32(auto trim) [DX0032]
MC9S08FL16MLC@LQFP32 [DX3001]
MC9S08FL16MLC@LQFP32(auto trim) [DX3001]
MC9S08FL16VBM@SDIP32 [DX0032]
MC9S08FL16VBM@SDIP32(auto trim) [DX0032]
MC9S08FL16VLC@LQFP32 [DX3001]
MC9S08FL16VLC@LQFP32(auto trim) [DX3001]
MC9S08FL8CBM@SDIP32 [DX0032]
MC9S08FL8CBM@SDIP32(auto trim) [DX0032]
MC9S08FL8CLC@LQFP32 [DX3001]
MC9S08FL8CLC@LQFP32(auto trim) [DX3001]
MC9S08FL8MBM@SDIP32 [DX0032]
MC9S08FL8MBM@SDIP32(auto trim) [DX0032]
MC9S08FL8MLC@LQFP32 [DX3001]
MC9S08FL8MLC@LQFP32(auto trim) [DX3001]
MC9S08FL8VBM@SDIP32 [DX0032]
MC9S08FL8VBM@SDIP32(auto trim) [DX0032]

MC9S08FL8VLC@LQFP32 [DX3001]
MC9S08FL8VLC@LQFP32(auto trim) [DX3001]

MC9S08GB32ACFU@LQFP64 [DX3011]	MC9S08GB32ACFUE@LQFP64 [DX3011]
MC9S08GB32AMFU@LQFP64 [DX3011]	MC9S08GB32AMFUE@LQFP64 [DX3011]
MC9S08GB32AVFU@LQFP64 [DX3011]	MC9S08GB32AVFUE@LQFP64 [DX3011]
MC9S08GB32CFU@LQFP64 [DX3011]	MC9S08GB32CFUE@LQFP64 [DX3011]
MC9S08GB32MFU@LQFP64 [DX3011]	MC9S08GB32MFUE@LQFP64 [DX3011]
MC9S08GB32VFU@LQFP64 [DX3011]	MC9S08GB32VFUE@LQFP64 [DX3011]
MC9S08GB60ACFU@LQFP64 [DX3011]	MC9S08GB60ACFUE@LQFP64 [DX3011]
MC9S08GB60AMFU@LQFP64 [DX3011]	MC9S08GB60AMFUE@LQFP64 [DX3011]
MC9S08GB60AVFU@LQFP64 [DX3011]	MC9S08GB60AVFUE@LQFP64 [DX3011]
MC9S08GB60CFU@LQFP64 [DX3011]	MC9S08GB60CFUE@LQFP64 [DX3011]
MC9S08GB60MFU@LQFP64 [DX3011]	MC9S08GB60MFUE@LQFP64 [DX3011]
MC9S08GB60VFU@LQFP64 [DX3011]	MC9S08GB60VFUE@LQFP64 [DX3011]
MC9S08GT16ACB@SDIP42 [DX0042]	MC9S08GT16ACBE@SDIP42 [DX0042]
MC9S08GT16ACFB@LQFP44 [DX3002]	MC9S08GT16ACFBE@LQFP44 [DX3002]
MC9S08GT16ACFC@MLF32 [DX4015]	MC9S08GT16ACFCE@MLF32 [DX4015]
MC9S08GT16ACFD@QFN48 [DX4021]	MC9S08GT16ACFDE@QFN48 [DX4021]
MC9S08GT16AMB@SDIP42 [DX0042]	MC9S08GT16AMBE@SDIP42 [DX0042]
MC9S08GT16AMFB@LQFP44 [DX3002]	MC9S08GT16AMFBE@LQFP44 [DX3002]
MC9S08GT16AMFC@MLF32 [DX4015]	MC9S08GT16AMFCE@MLF32 [DX4015]
MC9S08GT16AMFD@QFN48 [DX4021]	MC9S08GT16AMFDE@QFN48 [DX4021]
MC9S08GT16AVB@SDIP42 [DX0042]	MC9S08GT16AVBE@SDIP42 [DX0042]
MC9S08GT16AVFB@LQFP44 [DX3002]	MC9S08GT16AVFBE@LQFP44 [DX3002]
MC9S08GT16AVFC@MLF32 [DX4015]	MC9S08GT16AVFCE@MLF32 [DX4015]
MC9S08GT16AVFD@QFN48 [DX4021]	MC9S08GT16AVFDE@QFN48 [DX4021]
MC9S08GT16CB@SDIP42 [DX0042]	MC9S08GT16CBE@SDIP42 [DX0042]
MC9S08GT16CFB@LQFP44 [DX3002]	MC9S08GT16CFBE@LQFP44 [DX3002]
MC9S08GT16CFD@QFN48 [DX4021]	MC9S08GT16CFDE@QFN48 [DX4021]
MC9S08GT16MB@SDIP42 [DX0042]	MC9S08GT16MBE@SDIP42 [DX0042]
MC9S08GT16MFB@LQFP44 [DX3002]	MC9S08GT16MFBE@LQFP44 [DX3002]
MC9S08GT16MFD@QFN48 [DX4021]	MC9S08GT16MFDE@QFN48 [DX4021]
MC9S08GT16VB@SDIP42 [DX0042]	MC9S08GT16VBE@SDIP42 [DX0042]
MC9S08GT16VFB@LQFP44 [DX3002]	MC9S08GT16VFBE@LQFP44 [DX3002]
MC9S08GT16VFD@QFN48 [DX4021]	MC9S08GT16VFDE@QFN48 [DX4021]
MC9S08GT32ACB@SDIP42 [DX0042]	MC9S08GT32ACBE@SDIP42 [DX0042]
MC9S08GT32ACFB@LQFP44 [DX3002]	MC9S08GT32ACFBE@LQFP44 [DX3002]
MC9S08GT32ACFD@QFN48 [DX4021]	MC9S08GT32ACFDE@QFN48 [DX4021]
MC9S08GT32AMB@SDIP42 [DX0042]	MC9S08GT32AMBE@SDIP42 [DX0042]
MC9S08GT32AMFB@LQFP44 [DX3002]	MC9S08GT32AMFBE@LQFP44 [DX3002]
MC9S08GT32AMFD@QFN48 [DX4021]	MC9S08GT32AMFDE@QFN48 [DX4021]
MC9S08GT32AVB@SDIP42 [DX0042]	MC9S08GT32AVBE@SDIP42 [DX0042]
MC9S08GT32AVFB@LQFP44 [DX3002]	MC9S08GT32AVFBE@LQFP44 [DX3002]
MC9S08GT32AVFD@QFN48 [DX4021]	MC9S08GT32AVFDE@QFN48 [DX4021]
MC9S08GT32CB@SDIP42 [DX0042]	MC9S08GT32CBE@SDIP42 [DX0042]
MC9S08GT32CFB@LQFP44 [DX3002]	MC9S08GT32CFBE@LQFP44 [DX3002]
MC9S08GT32CFD@QFN48 [DX4021]	MC9S08GT32CFDE@QFN48 [DX4021]
MC9S08GT32MB@SDIP42 [DX0042]	MC9S08GT32MBE@SDIP42 [DX0042]

MC9S08GT32MFB@LQFP44 [DX3002]
MC9S08GT32MFBE@LQFP44 [DX3002]
MC9S08GT32MFD@QFN48 [DX4021]
MC9S08GT32MFDE@QFN48 [DX4021]
MC9S08GT32VB@SDIP42 [DX0042]
MC9S08GT32VBE@SDIP42 [DX0042]
MC9S08GT32VFB@LQFP44 [DX3002]
MC9S08GT32VFBE@LQFP44 [DX3002]
MC9S08GT32VFD@QFN48 [DX4021]
MC9S08GT32VFDE@QFN48 [DX4021]
MC9S08GT60ACB@SDIP42 [DX0042]
MC9S08GT60ACBE@SDIP42 [DX0042]
MC9S08GT60ACFB@LQFP44 [DX3002]
MC9S08GT60ACFBE@LQFP44 [DX3002]
MC9S08GT60ACFD@QFN48 [DX4021]
MC9S08GT60ACFDE@QFN48 [DX4021]
MC9S08GT60AMB@SDIP42 [DX0042]
MC9S08GT60AMBE@SDIP42 [DX0042]
MC9S08GT60AMFB@LQFP44 [DX3002]
MC9S08GT60AMFBE@LQFP44 [DX3002]
MC9S08GT60AMFD@QFN48 [DX4021]
MC9S08GT60AMFDE@QFN48 [DX4021]
MC9S08GT60AVB@SDIP42 [DX0042]
MC9S08GT60AVBE@SDIP42 [DX0042]
MC9S08GT60AVFB@LQFP44 [DX3002]
MC9S08GT60AVFBE@LQFP44 [DX3002]
MC9S08GT60AVFD@QFN48 [DX4021]
MC9S08GT60AVFDE@QFN48 [DX4021]
MC9S08GT60CB@SDIP42 [DX0042]
MC9S08GT60CBE@SDIP42 [DX0042]
MC9S08GT60CFB@LQFP44 [DX3002]
MC9S08GT60CFBE@LQFP44 [DX3002]
MC9S08GT60CFD@QFN48 [DX4021]
MC9S08GT60CFDE@QFN48 [DX4021]
MC9S08GT60MB@SDIP42 [DX0042]
MC9S08GT60MBE@SDIP42 [DX0042]
MC9S08GT60MFB@LQFP44 [DX3002]
MC9S08GT60MFBE@LQFP44 [DX3002]
MC9S08GT60MFD@QFN48 [DX4021]
MC9S08GT60MFDE@QFN48 [DX4021]
MC9S08GT60VB@SDIP42 [DX0042]
MC9S08GT60VBE@SDIP42 [DX0042]
MC9S08GT60VFB@LQFP44 [DX3002]
MC9S08GT60VFBE@LQFP44 [DX3002]
MC9S08GT60VFD@QFN48 [DX4021]
MC9S08GT60VFDE@QFN48 [DX4021]
MC9S08GT8ACB@SDIP42 [DX0042]
MC9S08GT8ACBE@SDIP42 [DX0042]
MC9S08GT8ACFB@LQFP44 [DX3002]
MC9S08GT8ACFBE@LQFP44 [DX3002]
MC9S08GT8ACFC@MLF32 [DX4015]
MC9S08GT8ACFCE@MLF32 [DX4015]
MC9S08GT8ACFD@QFN48 [DX4021]
MC9S08GT8ACFDE@QFN48 [DX4021]
MC9S08GT8AMB@SDIP42 [DX0042]
MC9S08GT8AMBE@SDIP42 [DX0042]
MC9S08GT8AMFB@LQFP44 [DX3002]
MC9S08GT8AMFBE@LQFP44 [DX3002]
MC9S08GT8AMFC@MLF32 [DX4015]
MC9S08GT8AMFCE@MLF32 [DX4015]
MC9S08GT8AMFD@QFN48 [DX4021]
MC9S08GT8AMFDE@QFN48 [DX4021]
MC9S08GT8AVB@SDIP42 [DX0042]
MC9S08GT8AVBE@SDIP42 [DX0042]
MC9S08GT8AVFB@LQFP44 [DX3002]
MC9S08GT8AVFBE@LQFP44 [DX3002]
MC9S08GT8AVFC@MLF32 [DX4015]
MC9S08GT8AVFCE@MLF32 [DX4015]
MC9S08GT8AVFD@QFN48 [DX4021]
MC9S08GT8AVFDE@QFN48 [DX4021]
MC9S08JE128CLH@QFP64 [DX3011]
MC9S08JE128CLK@QFP80 [DX3016]
MC9S08JE128MLH@QFP64 [DX3011]
MC9S08JE128MLK@QFP80 [DX3016]
MC9S08JE128VLH@QFP64 [DX3011]
MC9S08JE128VLK@QFP80 [DX3016]
MC9S08JE64CLH@QFP64 [DX3011]
MC9S08JE64MLH@QFP64 [DX3011]
MC9S08JE64VLH@QFP64 [DX3011]
MC9S08JM16CGT@QFN48 [DX4021]
MC9S08JM16CGTE@QFN48 [DX4021]
MC9S08JM16CLC@QFP32 [DX3001]
MC9S08JM16CLCE@QFP32 [DX3001]
MC9S08JM16CLD@QFP44 [DX3003]
MC9S08JM16CLDE@QFP44 [DX3003]
MC9S08JM16MGT@QFN48 [DX4021]
MC9S08JM16MGTE@QFN48 [DX4021]
MC9S08JM16MLC@QFP32 [DX3001]
MC9S08JM16MLCE@QFP32 [DX3001]
MC9S08JM16MLD@QFP44 [DX3003]
MC9S08JM16MLDE@QFP44 [DX3003]
MC9S08JM16VGT@QFN48 [DX4021]
MC9S08JM16VGTE@QFN48 [DX4021]
MC9S08JM16VLC@QFP32 [DX3001]
MC9S08JM16VLCE@QFP32 [DX3001]
MC9S08JM16VLD@QFP44 [DX3003]

MC9S08JM16VLDE@QFP44 [DX3003]
MC9S08JM32CGTE@QFN48 [DX4021]
MC9S08JM32CLDE@QFP44 [DX3003]
MC9S08JM32CLHE@QFP64 [DX3011]
MC9S08JM32CQHE@QFP64 [DX3014]
MC9S08JM32MGTE@QFN48 [DX4021]
MC9S08JM32MLDE@QFP44 [DX3003]
MC9S08JM32MLHE@QFP64 [DX3011]
MC9S08JM32MQHE@QFP64 [DX3014]
MC9S08JM32VGTE@QFN48 [DX4021]
MC9S08JM32VLDE@QFP44 [DX3003]
MC9S08JM32VLHE@QFP64 [DX3011]
MC9S08JM32VQHE@QFP64 [DX3014]
MC9S08JM60CGTE@QFN48 [DX4021]
MC9S08JM60CLDE@QFP44 [DX3003]
MC9S08JM60CLHE@QFP64 [DX3011]
MC9S08JM60CQHE@QFP64 [DX3014]
MC9S08JM60MGTE@QFN48 [DX4021]
MC9S08JM60MLDE@QFP44 [DX3003]
MC9S08JM60MLHE@QFP64 [DX3011]
MC9S08JM60MQHE@QFP64 [DX3014]
MC9S08JM60VGTE@QFN48 [DX4021]
MC9S08JM60VLDE@QFP44 [DX3003]
MC9S08JM60VLHE@QFP64 [DX3011]
MC9S08JM60VQHE@QFP64 [DX3014]
MC9S08JM8CGTE@QFN48 [DX4021]
MC9S08JM8CLCE@QFP32 [DX3001]
MC9S08JM8CLDE@QFP44 [DX3003]
MC9S08JM8MGTE@QFN48 [DX4021]
MC9S08JM8MLCE@QFP32 [DX3001]
MC9S08JM8MLDE@QFP44 [DX3003]
MC9S08JM8VGTE@QFN48 [DX4021]
MC9S08JM8VLCE@QFP32 [DX3001]
MC9S08JM8VLDE@QFP44 [DX3003]
MC9S08JS16CWJ@SOIC20 [DX1033]
MC9S08JS16LCWJ@SOIC20 [DX1033]
MC9S08JS16LMWJ@SOIC20 [DX1033]
MC9S08JS16LVWJ@SOIC20 [DX1033]
MC9S08JS16MWJ@SOIC20 [DX1033]
MC9S08JS16VWJ@SOIC20 [DX1033]
MC9S08JS8CWJ@SOIC20 [DX1033]
MC9S08JS8LCWJ@SOIC20 [DX1033]
MC9S08JS8LMWJ@SOIC20 [DX1033]
MC9S08JS8LVWJ@SOIC20 [DX1033]
MC9S08JS8MWJ@SOIC20 [DX1033]
MC9S08JS8VWJ@SOIC20 [DX1033]
MC9S08LC36LHE@QFP64 [DX3011]
MC9S08LC36LKE@QFP80 [DX3016]
MC9S08JM32CGT@QFN48 [DX4021]
MC9S08JM32CLD@QFP44 [DX3003]
MC9S08JM32CLH@QFP64 [DX3011]
MC9S08JM32CQH@QFP64 [DX3014]
MC9S08JM32MGT@QFN48 [DX4021]
MC9S08JM32MLD@QFP44 [DX3003]
MC9S08JM32MLH@QFP64 [DX3011]
MC9S08JM32MQH@QFP64 [DX3014]
MC9S08JM32VGT@QFN48 [DX4021]
MC9S08JM32VLD@QFP44 [DX3003]
MC9S08JM32VLH@QFP64 [DX3011]
MC9S08JM32VQH@QFP64 [DX3014]
MC9S08JM60CGT@QFN48 [DX4021]
MC9S08JM60CLD@QFP44 [DX3003]
MC9S08JM60CLH@QFP64 [DX3011]
MC9S08JM60CQH@QFP64 [DX3014]
MC9S08JM60MGT@QFN48 [DX4021]
MC9S08JM60MLD@QFP44 [DX3003]
MC9S08JM60MLH@QFP64 [DX3011]
MC9S08JM60MQH@QFP64 [DX3014]
MC9S08JM60VGT@QFN48 [DX4021]
MC9S08JM60VLD@QFP44 [DX3003]
MC9S08JM60VLH@QFP64 [DX3011]
MC9S08JM60VQH@QFP64 [DX3014]
MC9S08JM8CGT@QFN48 [DX4021]
MC9S08JM8CLC@QFP32 [DX3001]
MC9S08JM8CLD@QFP44 [DX3003]
MC9S08JM8MGT@QFN48 [DX4021]
MC9S08JM8MLC@QFP32 [DX3001]
MC9S08JM8MLD@QFP44 [DX3003]
MC9S08JM8VGT@QFN48 [DX4021]
MC9S08JM8VLC@QFP32 [DX3001]
MC9S08JM8VLD@QFP44 [DX3003]
MC9S08JS16CFK@QFN24 [DX4034]
MC9S08JS16LCFK@QFN24 [DX4034]
MC9S08JS16LMFK@QFN24 [DX4034]
MC9S08JS16LVFK@QFN24 [DX4034]
MC9S08JS16MFK@QFN24 [DX4034]
MC9S08JS16VFK@QFN24 [DX4034]
MC9S08JS8CFK@QFN24 [DX4034]
MC9S08JS8LCFK@QFN24 [DX4034]
MC9S08JS8LMFK@QFN24 [DX4034]
MC9S08JS8LVFK@QFN24 [DX4034]
MC9S08JS8MFK@QFN24 [DX4034]
MC9S08JS8VFK@QFN24 [DX4034]
MC9S08LC36LH@QFP64 [DX3011]
MC9S08LC36LK@QFP80 [DX3016]
MC9S08LC60LH@QFP64 [DX3011]

MC9S08LC60LHE@QFP64 [DX3011]
MC9S08LC60LK@QFP80 [DX3016]
MC9S08LC60LKE@QFP80 [DX3016]
MC9S08LG16CLF@QFP48 [DX3007]
MC9S08LG16CLF@QFP48(auto trim) [DX3007]
MC9S08LG16CLFE@QFP48 [DX3007]
MC9S08LG16CLFE@QFP48(auto trim) [DX3007]
MC9S08LG16CLH@QFP64 [DX3011]
MC9S08LG16CLH@QFP64(auto trim) [DX3011]
MC9S08LG16CLHE@QFP64 [DX3011]
MC9S08LG16CLHE@QFP64(auto trim) [DX3011]
MC9S08LG16MLF@QFP48 [DX3007]
MC9S08LG16MLF@QFP48(auto trim) [DX3007]
MC9S08LG16MLFE@QFP48 [DX3007]
MC9S08LG16MLFE@QFP48(auto trim) [DX3007]
MC9S08LG16MLH@QFP64 [DX3011]
MC9S08LG16MLH@QFP64(auto trim) [DX3011]
MC9S08LG16MLHE@QFP64 [DX3011]
MC9S08LG16MLHE@QFP64(auto trim) [DX3011]
MC9S08LG16VLF@QFP48 [DX3007]
MC9S08LG16VLF@QFP48(auto trim) [DX3007]
MC9S08LG16VLFE@QFP48 [DX3007]
MC9S08LG16VLFE@QFP48(auto trim) [DX3007]
MC9S08LG16VLH@QFP64 [DX3011]
MC9S08LG16VLH@QFP64(auto trim) [DX3011]
MC9S08LG16VLHE@QFP64 [DX3011]
MC9S08LG16VLHE@QFP64(auto trim) [DX3011]
MC9S08LG32CLF@QFP48 [DX3007]
MC9S08LG32CLF@QFP48(auto trim) [DX3007]
MC9S08LG32CLFE@QFP48 [DX3007]
MC9S08LG32CLFE@QFP48(auto trim) [DX3007]
MC9S08LG32CLH@QFP64 [DX3011]
MC9S08LG32CLH@QFP64(auto trim) [DX3011]
MC9S08LG32CLHE@QFP64 [DX3011]
MC9S08LG32CLHE@QFP64(auto trim) [DX3011]
MC9S08LG32CLK@QFP80 [DX3017]
MC9S08LG32CLK@QFP80(auto trim) [DX3017]
MC9S08LG32CLKE@QFP80 [DX3017]
MC9S08LG32CLKE@QFP80(auto trim) [DX3017]
MC9S08LG32MLF@QFP48 [DX3007]
MC9S08LG32MLF@QFP48(auto trim) [DX3007]
MC9S08LG32MLFE@QFP48 [DX3007]
MC9S08LG32MLFE@QFP48(auto trim) [DX3007]
MC9S08LG32MLH@QFP64 [DX3011]
MC9S08LG32MLH@QFP64(auto trim) [DX3011]
MC9S08LG32MLHE@QFP64 [DX3011]
MC9S08LG32MLHE@QFP64(auto trim) [DX3011]
MC9S08LG32MLK@QFP80 [DX3017]
MC9S08LG32MLK@QFP80(auto trim) [DX3017]
MC9S08LG32MLKE@QFP80 [DX3017]

MC9S08LG32MLKE@QFP80(auto trim) [DX3017]
MC9S08LG32VLF@QFP48 [DX3007]
MC9S08LG32VLF@QFP48(auto trim) [DX3007]
MC9S08LG32VLFE@QFP48 [DX3007]
MC9S08LG32VLFE@QFP48(auto trim) [DX3007]
MC9S08LG32VLH@QFP64 [DX3011]
MC9S08LG32VLH@QFP64(auto trim) [DX3011]
MC9S08LG32VLHE@QFP64 [DX3011]
MC9S08LG32VLHE@QFP64(auto trim) [DX3011]
MC9S08LG32VLK@QFP80 [DX3017]
MC9S08LG32VLK@QFP80(auto trim) [DX3017]
MC9S08LG32VLKE@QFP80 [DX3017]
MC9S08LG32VLKE@QFP80(auto trim) [DX3017]
MC9S08LL16CGT@QFN48 [DX4021]
MC9S08LL16CGT@QFN48(auto trim) [DX4021]
MC9S08LL16CLF@LQFP48 [DX3007]
MC9S08LL16CLF@LQFP48(auto trim) [DX3007]
MC9S08LL16CLH@LQFP64 [DX3011]
MC9S08LL16CLH@LQFP64(auto trim) [DX3011]
MC9S08LL16MGT@QFN48 [DX4021]
MC9S08LL16MGT@QFN48(auto trim) [DX4021]
MC9S08LL16MLF@LQFP48 [DX3007]
MC9S08LL16MLF@LQFP48(auto trim) [DX3007]
MC9S08LL16MLH@LQFP64 [DX3011]
MC9S08LL16MLH@LQFP64(auto trim) [DX3011]
MC9S08LL16VGT@QFN48 [DX4021]
MC9S08LL16VGT@QFN48(auto trim) [DX4021]
MC9S08LL16VLF@LQFP48 [DX3007]
MC9S08LL16VLF@LQFP48(auto trim) [DX3007]
MC9S08LL16VLH@LQFP64 [DX3011]
MC9S08LL16VLH@LQFP64(auto trim) [DX3011]
MC9S08LL64CLH@LQFP64 [DX3011]　　MC9S08LL64CLK@QFP80 [DX3017]
MC9S08LL64MLH@LQFP64 [DX3011]　　MC9S08LL64MLK@QFP80 [DX3017]
MC9S08LL64VLH@LQFP64 [DX3011]　　MC9S08LL64VLK@QFP80 [DX3017]
MC9S08LL8CGT@QFN48 [DX4021]
MC9S08LL8CGT@QFN48(auto trim) [DX4021]
MC9S08LL8CLF@LQFP48 [DX3007]
MC9S08LL8CLF@LQFP48(auto trim) [DX3007]
MC9S08LL8CLH@LQFP64 [DX3011]
MC9S08LL8CLH@LQFP64(auto trim) [DX3011]
MC9S08LL8MGT@QFN48 [DX4021]
MC9S08LL8MGT@QFN48(auto trim) [DX4021]
MC9S08LL8MLF@LQFP48 [DX3007]
MC9S08LL8MLF@LQFP48(auto trim) [DX3007]
MC9S08LL8MLH@LQFP64 [DX3011]
MC9S08LL8MLH@LQFP64(auto trim) [DX3011]
MC9S08LL8VGT@QFN48 [DX4021]
MC9S08LL8VGT@QFN48(auto trim) [DX4021]

MC9S08LL8VLF@LQFP48 [DX3007]
MC9S08LL8VLF@LQFP48(auto trim) [DX3007]
MC9S08LL8VLH@LQFP64 [DX3011]
MC9S08LL8VLH@LQFP64(auto trim) [DX3011]
MC9S08MP12CLC@QFP32 [DX3001]
MC9S08MP12CLF@QFP48 [DX3007]
MC9S08MP12CWL@SOIC28 [DX1033]
MC9S08MP12MLC@QFP32 [DX3001]
MC9S08MP12MLF@QFP48 [DX3007]
MC9S08MP12MWL@SOIC28 [DX1033]
MC9S08MP12VLC@QFP32 [DX3001]
MC9S08MP12VLF@QFP48 [DX3007]
MC9S08MP12VWL@SOIC28 [DX1033]
MC9S08MP16CLC@QFP32 [DX3001]
MC9S08MP16CLF@QFP48 [DX3007]
MC9S08MP16CWL@SOIC28 [DX1033]
MC9S08MP16MLC@QFP32 [DX3001]
MC9S08MP16MLF@QFP48 [DX3007]
MC9S08MP16MWL@SOIC28 [DX1033]
MC9S08MP16VLC@QFP32 [DX3001]
MC9S08MP16VLF@QFP48 [DX3007]
MC9S08MP16VWL@SOIC28 [DX1033]
MC9S08PA16CLC [DX3001]
MC9S08PA16CLD [DX3005]
MC9S08PA16CTG [DX1000]
MC9S08PA16CTJ [DX1000]
MC9S08PA16CWJ [DX1033]
MC9S08PA16VLC [DX3001]
MC9S08PA16VLD [DX3005]
MC9S08PA16VTG [DX1000]
MC9S08PA16VTJ [DX1000]
MC9S08PA16VWJ [DX1033]
MC9S08PA32CLC [DX3001]
MC9S08PA32CLD [DX3005]
MC9S08PA32CLF [DX3007]
MC9S08PA32CLH [DX3011]
MC9S08PA32CQH [DX3014]
MC9S08PA32VLC [DX3001]
MC9S08PA32VLD [DX3005]
MC9S08PA32VLF [DX3007]
MC9S08PA32VLH [DX3011]
MC9S08PA32VQH [DX3014]
MC9S08PA60CLC [DX3001]
MC9S08PA60CLD [DX3005]
MC9S08PA60CLF [DX3007]
MC9S08PA60CLH [DX3011]
MC9S08PA60CQH [DX3014]
MC9S08PA60VLC [DX3001]
MC9S08PA60VLD [DX3005]
MC9S08PA60VLF [DX3007]
MC9S08PA60VLH [DX3011]
MC9S08PA60VQH [DX3014]
MC9S08PA8CLC [DX3001]
MC9S08PA8CLD [DX3005]
MC9S08PA8CTG [DX1000]
MC9S08PA8CTJ [DX1000]
MC9S08PA8CWJ [DX1033]
MC9S08PA8VLC [DX3001]
MC9S08PA8VLD [DX3005]
MC9S08PA8VTG [DX1000]
MC9S08PA8VTJ [DX1000]
MC9S08PA8VWJ [DX1033]
MC9S08PT16CLC [DX3001]
MC9S08PT16CLD [DX3005]
MC9S08PT16CTG [DX1000]
MC9S08PT16CTJ [DX1000]
MC9S08PT16CWJ [DX1033]
MC9S08PT16VLC [DX3001]
MC9S08PT16VLD [DX3005]
MC9S08PT16VTG [DX1000]
MC9S08PT16VTJ [DX1000]
MC9S08PT16VWJ [DX1033]
MC9S08PT32CLC [DX3001]
MC9S08PT32CLD [DX3005]
MC9S08PT32CLF [DX3007]
MC9S08PT32CLH [DX3011]
MC9S08PT32CQH [DX3014]
MC9S08PT32VLC [DX3001]
MC9S08PT32VLD [DX3005]
MC9S08PT32VLF [DX3007]
MC9S08PT32VLH [DX3011]
MC9S08PT32VQH [DX3014]
MC9S08PT60CLC [DX3001]
MC9S08PT60CLD [DX3005]
MC9S08PT60CLF [DX3007]
MC9S08PT60CLH [DX3011]
MC9S08PT60CQH [DX3014]
MC9S08PT60VLC [DX3001]
MC9S08PT60VLD [DX3005]
MC9S08PT60VLF [DX3007]
MC9S08PT60VLH [DX3011]
MC9S08PT60VQH [DX3014]

MC9S08PT8CLC [DX3001]
MC9S08PT8CLD [DX3005]
MC9S08PT8CTG [DX1000]
MC9S08PT8CTJ [DX1000]
MC9S08PT8CWJ [DX1033]
MC9S08PT8VLC [DX3001]
MC9S08PT8VLD [DX3005]
MC9S08PT8VTG [DX1000]
MC9S08PT8VTJ [DX1000]
MC9S08PT8VWJ [DX1033]
MC9S08QA2CDN@SOIC8 [DX1030]
MC9S08QA2CDNE@SOIC8 [DX1030]
MC9S08QA2CFQ@DFN8 [DX4004]
MC9S08QA2CFQE@DFN8 [DX4004]
MC9S08QA2CPA
MC9S08QA2CPAE
MC9S08QA2MDN@SOIC8 [DX1030]
MC9S08QA2MDNE@SOIC8 [DX1030]
MC9S08QA2MFQ@DFN8 [DX4004]
MC9S08QA2MFQE@DFN8 [DX4004]
MC9S08QA2MPA
MC9S08QA2MPAE
MC9S08QA2VDN@SOIC8 [DX1030]
MC9S08QA2VDNE@SOIC8 [DX1030]
MC9S08QA2VFQ@DFN8 [DX4004]
MC9S08QA2VFQE@DFN8 [DX4004]
MC9S08QA2VPA
MC9S08QA2VPAE
MC9S08QA4CDN@SOIC8 [DX1030]
MC9S08QA4CDNE@SOIC8 [DX1030]
MC9S08QA4CFQ@DFN8 [DX4004]
MC9S08QA4CFQE@DFN8 [DX4004]
MC9S08QA4CPA
MC9S08QA4CPAE
MC9S08QA4MDN@SOIC8 [DX1030]
MC9S08QA4MDNE@SOIC8 [DX1030]
MC9S08QA4MFQ@DFN8 [DX4004]
MC9S08QA4MFQE@DFN8 [DX4004]
MC9S08QA4MPA
MC9S08QA4MPAE
MC9S08QA4VDN@SOIC8 [DX1030]
MC9S08QA4VDNE@SOIC8 [DX1030]
MC9S08QA4VFQ@DFN8 [DX4004]
MC9S08QA4VFQE@DFN8 [DX4004]
MC9S08QA4VPA
MC9S08QA4VPAE
MC9S08QB4CGK@QFN24 [DX4034]
MC9S08QB4CTG@TSSOP16 [DX1001]
MC9S08QB4CWL@SOIC28 [DX1033]
MC9S08QB4MGK@QFN24 [DX4034]
MC9S08QB4MTG@TSSOP16 [DX1001]
MC9S08QB4MWL@SOIC28 [DX1033]
MC9S08QB4VGK@QFN24 [DX4034]
MC9S08QB4VTG@TSSOP16 [DX1001]
MC9S08QB4VWL@SOIC28 [DX1033]
MC9S08QB8CGK@QFN24 [DX4034]
MC9S08QB8CTG@TSSOP16 [DX1001]
MC9S08QB8CWL@SOIC28 [DX1033]
MC9S08QB8MGK@QFN24 [DX4034]
MC9S08QB8MTG@TSSOP16 [DX1001]
MC9S08QB8MWL@SOIC28 [DX1033]
MC9S08QB8VGK@QFN24 [DX4034]
MC9S08QB8VTG@TSSOP16 [DX1001]
MC9S08QB8VWL@SOIC28 [DX1033]
MC9S08QD2CPC
MC9S08QD2CPC(auto trim)
MC9S08QD2CPCE
MC9S08QD2CPCE(auto trim)
MC9S08QD2CSC@SOIC8 [DX1016]
MC9S08QD2CSC@SOIC8(auto trim) [DX1016]
MC9S08QD2CSCE@SOIC8 [DX1016]
MC9S08QD2CSCE@SOIC8(auto trim) [DX1016]
MC9S08QD2MPC
MC9S08QD2MPC(auto trim)
MC9S08QD2MPCE
MC9S08QD2MPCE(auto trim)
MC9S08QD2MSC@SOIC8 [DX1016]
MC9S08QD2MSC@SOIC8(auto trim) [DX1016]
MC9S08QD2MSCE@SOIC8 [DX1016]
MC9S08QD2MSCE@SOIC8(auto trim) [DX1016]
MC9S08QD2VPC
MC9S08QD2VPC(auto trim)
MC9S08QD2VPCE
MC9S08QD2VPCE(auto trim)
MC9S08QD2VSC@SOIC8 [DX1016]
MC9S08QD2VSC@SOIC8(auto trim) [DX1016]

MC9S08QD2VSCE@SOIC8 [DX1016]
MC9S08QD2VSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4CPC MC9S08QD4CPC(auto trim)
MC9S08QD4CPCE MC9S08QD4CPCE(auto trim)
MC9S08QD4CSC@SOIC8 [DX1016]
MC9S08QD4CSC@SOIC8(auto trim) [DX1016]
MC9S08QD4CSCE@SOIC8 [DX1016]
MC9S08QD4CSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4MPC MC9S08QD4MPC(auto trim)
MC9S08QD4MPCE MC9S08QD4MPCE(auto trim)
MC9S08QD4MSC@SOIC8 [DX1016]
MC9S08QD4MSC@SOIC8(auto trim) [DX1016]
MC9S08QD4MSCE@SOIC8 [DX1016]
MC9S08QD4MSCE@SOIC8(auto trim) [DX1016]
MC9S08QD4VPC MC9S08QD4VPC(auto trim)
MC9S08QD4VPCE MC9S08QD4VPCE(auto trim)
MC9S08QD4VSC@SOIC8 [DX1016]
MC9S08QD4VSC@SOIC8(auto trim) [DX1016]
MC9S08QD4VSCE@SOIC8 [DX1016]
MC9S08QD4VSCE@SOIC8(auto trim) [DX1016]
MC9S08QE128CFT@QFN48 [DX4021] MC9S08QE128CFTE@QFN48 [DX4021]
MC9S08QE128CLC@QFP32 [DX3001] MC9S08QE128CLCE@QFP32 [DX3001]
MC9S08QE128CLD@QFP44 [DX3005] MC9S08QE128CLDE@QFP44 [DX3005]
MC9S08QE128CLH@QFP64 [DX3011] MC9S08QE128CLHE@QFP64 [DX3011]
MC9S08QE128CLK@QFP80 [DX3017] MC9S08QE128CLKE@QFP80 [DX3017]
MC9S08QE128MFT@QFN48 [DX4021] MC9S08QE128MFTE@QFN48 [DX4021]
MC9S08QE128MLC@QFP32 [DX3001] MC9S08QE128MLCE@QFP32 [DX3001]
MC9S08QE128MLD@QFP44 [DX3005] MC9S08QE128MLDE@QFP44 [DX3005]
MC9S08QE128MLH@QFP64 [DX3011] MC9S08QE128MLHE@QFP64 [DX3011]
MC9S08QE128MLK@QFP80 [DX3017] MC9S08QE128MLKE@QFP80 [DX3017]
MC9S08QE128VFT@QFN48 [DX4021] MC9S08QE128VFTE@QFN48 [DX4021]
MC9S08QE128VLC@QFP32 [DX3001] MC9S08QE128VLCE@QFP32 [DX3001]
MC9S08QE128VLD@QFP44 [DX3005] MC9S08QE128VLDE@QFP44 [DX3005]
MC9S08QE128VLH@QFP64 [DX3011] MC9S08QE128VLHE@QFP64 [DX3011]
MC9S08QE128VLK@QFP80 [DX3017] MC9S08QE128VLKE@QFP80 [DX3017]
MC9S08QE16CFT@QFN48 [DX4021]
MC9S08QE16CFT@QFN48(auto trim) [DX4021]
MC9S08QE16CFTE@QFN48 [DX4021]
MC9S08QE16CFTE@QFN48(auto trim) [DX4021]
MC9S08QE16CLC@QFP32 [DX3001]
MC9S08QE16CLC@QFP32(auto trim) [DX3001]
MC9S08QE16CLCE@QFP32 [DX3001]
MC9S08QE16CLCE@QFP32(auto trim) [DX3001]
MC9S08QE16CLD@QFP44 [DX3005]
MC9S08QE16CLD@QFP44(auto trim) [DX3005]
MC9S08QE16CLDE@QFP44 [DX3005]
MC9S08QE16CLDE@QFP44(auto trim) [DX3005]
MC9S08QE16CWL@SOIC28 [DX1033]

MC9S08QE16CWL@SOIC28(auto trim) [DX1033]
MC9S08QE16CWLE@SOIC28 [DX1033]
MC9S08QE16CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE16MFT@QFN48 [DX4021]
MC9S08QE16MFT@QFN48(auto trim) [DX4021]
MC9S08QE16MFTE@QFN48 [DX4021]
MC9S08QE16MFTE@QFN48(auto trim) [DX4021]
MC9S08QE16MLC@QFP32 [DX3001]
MC9S08QE16MLC@QFP32(auto trim) [DX3001]
MC9S08QE16MLCE@QFP32 [DX3001]
MC9S08QE16MLCE@QFP32(auto trim) [DX3001]
MC9S08QE16MLD@QFP44 [DX3005]
MC9S08QE16MLD@QFP44(auto trim) [DX3005]
MC9S08QE16MLDE@QFP44 [DX3005]
MC9S08QE16MLDE@QFP44(auto trim) [DX3005]
MC9S08QE16MWL@SOIC28 [DX1033]
MC9S08QE16MWL@SOIC28(auto trim) [DX1033]
MC9S08QE16MWLE@SOIC28 [DX1033]
MC9S08QE16MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE16VFT@QFN48 [DX4021]
MC9S08QE16VFT@QFN48(auto trim) [DX4021]
MC9S08QE16VFTE@QFN48 [DX4021]
MC9S08QE16VFTE@QFN48(auto trim) [DX4021]
MC9S08QE16VLC@QFP32 [DX3001]
MC9S08QE16VLC@QFP32(auto trim) [DX3001]
MC9S08QE16VLCE@QFP32 [DX3001]
MC9S08QE16VLCE@QFP32(auto trim) [DX3001]
MC9S08QE16VLD@QFP44 [DX3005]
MC9S08QE16VLD@QFP44(auto trim) [DX3005]
MC9S08QE16VLDE@QFP44 [DX3005]
MC9S08QE16VLDE@QFP44(auto trim) [DX3005]
MC9S08QE16VWL@SOIC28 [DX1033]
MC9S08QE16VWL@SOIC28(auto trim) [DX1033]
MC9S08QE16VWLE@SOIC28 [DX1033]
MC9S08QE16VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32CFT@QFN48 [DX4021]
MC9S08QE32CFT@QFN48(auto trim) [DX4021]
MC9S08QE32CFTE@QFN48 [DX4021]
MC9S08QE32CFTE@QFN48(auto trim) [DX4021]
MC9S08QE32CLC@QFP32 [DX3001]
MC9S08QE32CLC@QFP32(auto trim) [DX3001]
MC9S08QE32CLCE@QFP32 [DX3001]
MC9S08QE32CLCE@QFP32(auto trim) [DX3001]
MC9S08QE32CLD@QFP44 [DX3005]
MC9S08QE32CLD@QFP44(auto trim) [DX3005]
MC9S08QE32CLDE@QFP44 [DX3005]
MC9S08QE32CLDE@QFP44(auto trim) [DX3005]
MC9S08QE32CWL@SOIC28 [DX1033]

MC9S08QE32CWL@SOIC28(auto trim) [DX1033]
MC9S08QE32CWLE@SOIC28 [DX1033]
MC9S08QE32CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32MFT@QFN48 [DX4021]
MC9S08QE32MFT@QFN48(auto trim) [DX4021]
MC9S08QE32MFTE@QFN48 [DX4021]
MC9S08QE32MFTE@QFN48(auto trim) [DX4021]
MC9S08QE32MLC@QFP32 [DX3001]
MC9S08QE32MLC@QFP32(auto trim) [DX3001]
MC9S08QE32MLCE@QFP32 [DX3001]
MC9S08QE32MLCE@QFP32(auto trim) [DX3001]
MC9S08QE32MLD@QFP44 [DX3005]
MC9S08QE32MLD@QFP44(auto trim) [DX3005]
MC9S08QE32MLDE@QFP44 [DX3005]
MC9S08QE32MLDE@QFP44(auto trim) [DX3005]
MC9S08QE32MWL@SOIC28 [DX1033]
MC9S08QE32MWL@SOIC28(auto trim) [DX1033]
MC9S08QE32MWLE@SOIC28 [DX1033]
MC9S08QE32MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE32VFT@QFN48 [DX4021]
MC9S08QE32VFT@QFN48(auto trim) [DX4021]
MC9S08QE32VFTE@QFN48 [DX4021]
MC9S08QE32VFTE@QFN48(auto trim) [DX4021]
MC9S08QE32VLC@QFP32 [DX3001]
MC9S08QE32VLC@QFP32(auto trim) [DX3001]
MC9S08QE32VLCE@QFP32 [DX3001]
MC9S08QE32VLCE@QFP32(auto trim) [DX3001]
MC9S08QE32VLD@QFP44 [DX3005]
MC9S08QE32VLD@QFP44(auto trim) [DX3005]
MC9S08QE32VLDE@QFP44 [DX3005]
MC9S08QE32VLDE@QFP44(auto trim) [DX3005]
MC9S08QE32VWL@SOIC28 [DX1033]
MC9S08QE32VWL@SOIC28(auto trim) [DX1033]
MC9S08QE32VWLE@SOIC28 [DX1033]
MC9S08QE32VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4CLC@QFP32 [DX3001]
MC9S08QE4CLC@QFP32(auto trim) [DX3001]
MC9S08QE4CLCE@QFP32 [DX3001]
MC9S08QE4CLCE@QFP32(auto trim) [DX3001]
MC9S08QE4CPG MC9S08QE4CPG(auto trim)
MC9S08QE4CPGE MC9S08QE4CPGE(auto trim)
MC9S08QE4CTG@TSSOP16 [DX1000]
MC9S08QE4CTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4CTGE@TSSOP16 [DX1000]
MC9S08QE4CTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4CWJ@SOIC20 [DX1033]
MC9S08QE4CWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4CWJE@SOIC20 [DX1033]

MC9S08QE4CWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4CWL@SOIC28 [DX1033]
MC9S08QE4CWL@SOIC28(auto trim) [DX1033]
MC9S08QE4CWLE@SOIC28 [DX1033]
MC9S08QE4CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4MLC@QFP32 [DX3001]
MC9S08QE4MLC@QFP32(auto trim) [DX3001]
MC9S08QE4MLCE@QFP32 [DX3001]
MC9S08QE4MLCE@QFP32(auto trim) [DX3001]
MC9S08QE4MPG MC9S08QE4MPG(auto trim)
MC9S08QE4MPGE MC9S08QE4MPGE(auto trim)
MC9S08QE4MTG@TSSOP16 [DX1000]
MC9S08QE4MTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4MTGE@TSSOP16 [DX1000]
MC9S08QE4MTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4MWJ@SOIC20 [DX1033]
MC9S08QE4MWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4MWJE@SOIC20 [DX1033]
MC9S08QE4MWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4MWL@SOIC28 [DX1033]
MC9S08QE4MWL@SOIC28(auto trim) [DX1033]
MC9S08QE4MWLE@SOIC28 [DX1033]
MC9S08QE4MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE4VLC@QFP32 [DX3001]
MC9S08QE4VLC@QFP32(auto trim) [DX3001]
MC9S08QE4VLCE@QFP32 [DX3001]
MC9S08QE4VLCE@QFP32(auto trim) [DX3001]
MC9S08QE4VPG MC9S08QE4VPG(auto trim)
MC9S08QE4VPGE MC9S08QE4VPGE(auto trim)
MC9S08QE4VTG@TSSOP16 [DX1000]
MC9S08QE4VTG@TSSOP16(auto trim) [DX1000]
MC9S08QE4VTGE@TSSOP16 [DX1000]
MC9S08QE4VTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE4VWJ@SOIC20 [DX1033]
MC9S08QE4VWJ@SOIC20(auto trim) [DX1033]
MC9S08QE4VWJE@SOIC20 [DX1033]
MC9S08QE4VWJE@SOIC20(auto trim) [DX1033]
MC9S08QE4VWL@SOIC28 [DX1033]
MC9S08QE4VWL@SOIC28(auto trim) [DX1033]
MC9S08QE4VWLE@SOIC28 [DX1033]
MC9S08QE4VWLE@SOIC28(auto trim) [DX1033]
MC9S08QE64CFT@QFN48 [DX4021] MC9S08QE64CFTE@QFN48 [DX4021]
MC9S08QE64CLC@QFP32 [DX3001] MC9S08QE64CLCE@QFP32 [DX3001]
MC9S08QE64CLD@QFP44 [DX3005] MC9S08QE64CLDE@QFP44 [DX3005]
MC9S08QE64CLH@QFP64 [DX3011] MC9S08QE64CLHE@QFP64 [DX3011]
MC9S08QE64CLK@QFP80 [DX3017] MC9S08QE64CLKE@QFP80 [DX3017]
MC9S08QE64MFT@QFN48 [DX4021] MC9S08QE64MFTE@QFN48 [DX4021]
MC9S08QE64MLC@QFP32 [DX3001] MC9S08QE64MLCE@QFP32 [DX3001]

MC9S08QE64MLD@QFP44 [DX3005]
MC9S08QE64MLDE@QFP44 [DX3005]
MC9S08QE64MLH@QFP64 [DX3011]
MC9S08QE64MLHE@QFP64 [DX3011]
MC9S08QE64MLK@QFP80 [DX3017]
MC9S08QE64MLKE@QFP80 [DX3017]
MC9S08QE64VFT@QFN48 [DX4021]
MC9S08QE64VFTE@QFN48 [DX4021]
MC9S08QE64VLC@QFP32 [DX3001]
MC9S08QE64VLCE@QFP32 [DX3001]
MC9S08QE64VLD@QFP44 [DX3005]
MC9S08QE64VLDE@QFP44 [DX3005]
MC9S08QE64VLH@QFP64 [DX3011]
MC9S08QE64VLHE@QFP64 [DX3011]
MC9S08QE64VLK@QFP80 [DX3017]
MC9S08QE64VLKE@QFP80 [DX3017]
MC9S08QE8CLC@QFP32 [DX3001]
MC9S08QE8CLC@QFP32(auto trim) [DX3001]
MC9S08QE8CLCE@QFP32 [DX3001]
MC9S08QE8CLCE@QFP32(auto trim) [DX3001]
MC9S08QE8CPG
MC9S08QE8CPG(auto trim)
MC9S08QE8CPGE
MC9S08QE8CPGE(auto trim)
MC9S08QE8CTG@TSSOP16 [DX1000]
MC9S08QE8CTG@TSSOP16(auto trim) [DX1000]
MC9S08QE8CTGE@TSSOP16 [DX1000]
MC9S08QE8CTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE8CWJ@SOIC20 [DX1033]
MC9S08QE8CWJ@SOIC20(auto trim) [DX1033]
MC9S08QE8CWJE@SOIC20 [DX1033]
MC9S08QE8CWJE@SOIC20(auto trim) [DX1033]
MC9S08QE8CWL@SOIC28 [DX1033]
MC9S08QE8CWL@SOIC28(auto trim) [DX1033]
MC9S08QE8CWLE@SOIC28 [DX1033]
MC9S08QE8CWLE@SOIC28(auto trim) [DX1033]
MC9S08QE8MLC@QFP32 [DX3001]
MC9S08QE8MLC@QFP32(auto trim) [DX3001]
MC9S08QE8MLCE@QFP32 [DX3001]
MC9S08QE8MLCE@QFP32(auto trim) [DX3001]
MC9S08QE8MPG
MC9S08QE8MPG(auto trim)
MC9S08QE8MPGE
MC9S08QE8MPGE(auto trim)
MC9S08QE8MTG@TSSOP16 [DX1000]
MC9S08QE8MTG@TSSOP16(auto trim) [DX1000]
MC9S08QE8MTGE@TSSOP16 [DX1000]
MC9S08QE8MTGE@TSSOP16(auto trim) [DX1000]
MC9S08QE8MWJ@SOIC20 [DX1033]
MC9S08QE8MWJ@SOIC20(auto trim) [DX1033]
MC9S08QE8MWJE@SOIC20 [DX1033]
MC9S08QE8MWJE@SOIC20(auto trim) [DX1033]
MC9S08QE8MWL@SOIC28 [DX1033]
MC9S08QE8MWL@SOIC28(auto trim) [DX1033]
MC9S08QE8MWLE@SOIC28 [DX1033]
MC9S08QE8MWLE@SOIC28(auto trim) [DX1033]
MC9S08QE8VLC@QFP32 [DX3001]
MC9S08QE8VLC@QFP32(auto trim) [DX3001]
MC9S08QE8VLCE@QFP32 [DX3001]
MC9S08QE8VLCE@QFP32(auto trim) [DX3001]

MC9S08QE8VPG	MC9S08QE8VPG(auto trim)
MC9S08QE8VPGE	MC9S08QE8VPGE(auto trim)
MC9S08QE8VTG@TSSOP16 [DX1000]	
MC9S08QE8VTG@TSSOP16(auto trim) [DX1000]	
MC9S08QE8VTGE@TSSOP16 [DX1000]	
MC9S08QE8VTGE@TSSOP16(auto trim) [DX1000]	
MC9S08QE8VWJ@SOIC20 [DX1033]	
MC9S08QE8VWJ@SOIC20(auto trim) [DX1033]	
MC9S08QE8VWJE@SOIC20 [DX1033]	
MC9S08QE8VWJE@SOIC20(auto trim) [DX1033]	
MC9S08QE8VWL@SOIC28 [DX1033]	
MC9S08QE8VWL@SOIC28(auto trim) [DX1033]	
MC9S08QE8VWLE@SOIC28 [DX1033]	
MC9S08QE8VWLE@SOIC28(auto trim) [DX1033]	
MC9S08QE96CFT@QFN48 [DX4021]	MC9S08QE96CFTE@QFN48 [DX4021]
MC9S08QE96CLC@QFP32 [DX3001]	MC9S08QE96CLCE@QFP32 [DX3001]
MC9S08QE96CLD@QFP44 [DX3005]	MC9S08QE96CLDE@QFP44 [DX3005]
MC9S08QE96CLH@QFP64 [DX3011]	MC9S08QE96CLHE@QFP64 [DX3011]
MC9S08QE96CLK@QFP80 [DX3017]	MC9S08QE96CLKE@QFP80 [DX3017]
MC9S08QE96MFT@QFN48 [DX4021]	MC9S08QE96MFTE@QFN48 [DX4021]
MC9S08QE96MLC@QFP32 [DX3001]	MC9S08QE96MLCE@QFP32 [DX3001]
MC9S08QE96MLD@QFP44 [DX3005]	MC9S08QE96MLDE@QFP44 [DX3005]
MC9S08QE96MLH@QFP64 [DX3011]	MC9S08QE96MLHE@QFP64 [DX3011]
MC9S08QE96MLK@QFP80 [DX3017]	MC9S08QE96MLKE@QFP80 [DX3017]
MC9S08QE96VFT@QFN48 [DX4021]	MC9S08QE96VFTE@QFN48 [DX4021]
MC9S08QE96VLC@QFP32 [DX3001]	MC9S08QE96VLCE@QFP32 [DX3001]
MC9S08QE96VLD@QFP44 [DX3005]	MC9S08QE96VLDE@QFP44 [DX3005]
MC9S08QE96VLH@QFP64 [DX3011]	MC9S08QE96VLHE@QFP64 [DX3011]
MC9S08QE96VLK@QFP80 [DX3017]	MC9S08QE96VLKE@QFP80 [DX3017]
MC9S08QG4CDN@SOIC8 [DX1030]	MC9S08QG4CDNE@SOIC8 [DX1030]
MC9S08QG4CDT@TSSOP16 [DX1000]	MC9S08QG4CDTE@TSSOP16 [DX1000]
MC9S08QG4CFF@QFN16 [DX4009]	MC9S08QG4CFFE@QFN16 [DX4009]
MC9S08QG4CFQ@DFN8 [DX4004]	MC9S08QG4CFQE@DFN8 [DX4004]
MC9S08QG4CPA	MC9S08QG4CPAE
MC9S08QG4MDN@SOIC8 [DX1030]	MC9S08QG4MDNE@SOIC8 [DX1030]
MC9S08QG4MDT@TSSOP16 [DX1000]	MC9S08QG4MDTE@TSSOP16 [DX1000]
MC9S08QG4MFF@QFN16 [DX4009]	MC9S08QG4MFFE@QFN16 [DX4009]
MC9S08QG4MFQ@DFN8 [DX4004]	MC9S08QG4MFQE@DFN8 [DX4004]
MC9S08QG4MPA	MC9S08QG4MPAE
MC9S08QG4VDN@SOIC8 [DX1030]	MC9S08QG4VDNE@SOIC8 [DX1030]
MC9S08QG4VDT@TSSOP16 [DX1000]	MC9S08QG4VDTE@TSSOP16 [DX1000]
MC9S08QG4VFF@QFN16 [DX4009]	MC9S08QG4VFFE@QFN16 [DX4009]
MC9S08QG4VFQ@DFN8 [DX4004]	MC9S08QG4VFQE@DFN8 [DX4004]
MC9S08QG4VPA	MC9S08QG4VPAE
MC9S08QG8CDN@SOIC8 [DX1030]	MC9S08QG8CDNE@SOIC8 [DX1030]
MC9S08QG8CDT@TSSOP16 [DX1000]	MC9S08QG8CDTE@TSSOP16 [DX1000]
MC9S08QG8CFF@QFN16 [DX4009]	MC9S08QG8CFFE@QFN16 [DX4009]
MC9S08QG8CFQ@DFN8 [DX4004]	MC9S08QG8CFQE@DFN8 [DX4004]

MC9S08QG8CPB	MC9S08QG8CPBE
MC9S08QG8MDN@SOIC8 [DX1030]	MC9S08QG8MDNE@SOIC8 [DX1030]
MC9S08QG8MDT@TSSOP16 [DX1000]	MC9S08QG8MDTE@TSSOP16 [DX1000]
MC9S08QG8MFF@QFN16 [DX4009]	MC9S08QG8MFFE@QFN16 [DX4009]
MC9S08QG8MFQ@DFN8 [DX4004]	MC9S08QG8MFQE@DFN8 [DX4004]
MC9S08QG8MPB	MC9S08QG8MPBE
MC9S08QG8VDN@SOIC8 [DX1030]	MC9S08QG8VDNE@SOIC8 [DX1030]
MC9S08QG8VDT@TSSOP16 [DX1000]	MC9S08QG8VDTE@TSSOP16 [DX1000]
MC9S08QG8VFF@QFN16 [DX4009]	MC9S08QG8VFFE@QFN16 [DX4009]
MC9S08QG8VFQ@DFN8 [DX4004]	MC9S08QG8VFQE@DFN8 [DX4004]
MC9S08QG8VPB	MC9S08QG8VPBE
MC9S08RC16CDW@SOIC28 [DX1033]	MC9S08RC16CDWE@SOIC28 [DX1033]
MC9S08RC16CFD@QFN48 [DX4021]	MC9S08RC16CFDE@QFN48 [DX4021]
MC9S08RC16CFG@LQFP44 [DX3003]	MC9S08RC16CFGE@LQFP44 [DX3003]
MC9S08RC16CFJ@LQFP32 [DX3001]	MC9S08RC16CFJE@LQFP32 [DX3001]
MC9S08RC16CP	MC9S08RC16CPE
MC9S08RC16MDW@SOIC28 [DX1033]	MC9S08RC16MDWE@SOIC28 [DX1033]
MC9S08RC16MFD@QFN48 [DX4021]	MC9S08RC16MFDE@QFN48 [DX4021]
MC9S08RC16MFG@LQFP44 [DX3003]	MC9S08RC16MFGE@LQFP44 [DX3003]
MC9S08RC16MFJ@LQFP32 [DX3001]	MC9S08RC16MFJE@LQFP32 [DX3001]
MC9S08RC16MP	MC9S08RC16MPE
MC9S08RC16VDW@SOIC28 [DX1033]	MC9S08RC16VDWE@SOIC28 [DX1033]
MC9S08RC16VFD@QFN48 [DX4021]	MC9S08RC16VFDE@QFN48 [DX4021]
MC9S08RC16VFG@LQFP44 [DX3003]	MC9S08RC16VFGE@LQFP44 [DX3003]
MC9S08RC16VFJ@LQFP32 [DX3001]	MC9S08RC16VFJE@LQFP32 [DX3001]
MC9S08RC16VP	MC9S08RC16VPE
MC9S08RC32CDW@SOIC28 [DX1033]	MC9S08RC32CDWE@SOIC28 [DX1033]
MC9S08RC32CFD@QFN48 [DX4021]	MC9S08RC32CFDE@QFN48 [DX4021]
MC9S08RC32CFG@LQFP44 [DX3003]	MC9S08RC32CFGE@LQFP44 [DX3003]
MC9S08RC32CFJ@LQFP32 [DX3001]	MC9S08RC32CFJE@LQFP32 [DX3001]
MC9S08RC32CP	MC9S08RC32CPE
MC9S08RC32MDW@SOIC28 [DX1033]	MC9S08RC32MDWE@SOIC28 [DX1033]
MC9S08RC32MFD@QFN48 [DX4021]	MC9S08RC32MFDE@QFN48 [DX4021]
MC9S08RC32MFG@LQFP44 [DX3003]	MC9S08RC32MFGE@LQFP44 [DX3003]
MC9S08RC32MFJ@LQFP32 [DX3001]	MC9S08RC32MFJE@LQFP32 [DX3001]
MC9S08RC32MP	MC9S08RC32MPE
MC9S08RC32VDW@SOIC28 [DX1033]	MC9S08RC32VDWE@SOIC28 [DX1033]
MC9S08RC32VFD@QFN48 [DX4021]	MC9S08RC32VFDE@QFN48 [DX4021]
MC9S08RC32VFG@LQFP44 [DX3003]	MC9S08RC32VFGE@LQFP44 [DX3003]
MC9S08RC32VFJ@LQFP32 [DX3001]	MC9S08RC32VFJE@LQFP32 [DX3001]
MC9S08RC32VP	MC9S08RC32VPE
MC9S08RC60CDW@SOIC28 [DX1033]	MC9S08RC60CDWE@SOIC28 [DX1033]
MC9S08RC60CFD@QFN48 [DX4021]	MC9S08RC60CFDE@QFN48 [DX4021]
MC9S08RC60CFG@LQFP44 [DX3003]	MC9S08RC60CFGE@LQFP44 [DX3003]
MC9S08RC60CFJ@LQFP32 [DX3001]	MC9S08RC60CFJE@LQFP32 [DX3001]
MC9S08RC60CP	MC9S08RC60CPE
MC9S08RC60MDW@SOIC28 [DX1033]	MC9S08RC60MDWE@SOIC28 [DX1033]
MC9S08RC60MFD@QFN48 [DX4021]	MC9S08RC60MFDE@QFN48 [DX4021]

MC9S08RC60MFG@LQFP44 [DX3003]	MC9S08RC60MFGE@LQFP44 [DX3003]
MC9S08RC60MFJ@LQFP32 [DX3001]	MC9S08RC60MFJE@LQFP32 [DX3001]
MC9S08RC60MP	MC9S08RC60MPE
MC9S08RC60VDW@SOIC28 [DX1033]	MC9S08RC60VDWE@SOIC28 [DX1033]
MC9S08RC60VFD@QFN48 [DX4021]	MC9S08RC60VFDE@QFN48 [DX4021]
MC9S08RC60VFG@LQFP44 [DX3003]	MC9S08RC60VFGE@LQFP44 [DX3003]
MC9S08RC60VFJ@LQFP32 [DX3001]	MC9S08RC60VFJE@LQFP32 [DX3001]
MC9S08RC60VP	MC9S08RC60VPE
MC9S08RC8CDW@SOIC28 [DX1033]	MC9S08RC8CDWE@SOIC28 [DX1033]
MC9S08RC8CFD@QFN48 [DX4021]	MC9S08RC8CFDE@QFN48 [DX4021]
MC9S08RC8CFG@LQFP44 [DX3003]	MC9S08RC8CFGE@LQFP44 [DX3003]
MC9S08RC8CFJ@LQFP32 [DX3001]	MC9S08RC8CFJE@LQFP32 [DX3001]
MC9S08RC8CP	MC9S08RC8CPE
MC9S08RC8MDW@SOIC28 [DX1033]	MC9S08RC8MDWE@SOIC28 [DX1033]
MC9S08RC8MFD@QFN48 [DX4021]	MC9S08RC8MFDE@QFN48 [DX4021]
MC9S08RC8MFG@LQFP44 [DX3003]	MC9S08RC8MFGE@LQFP44 [DX3003]
MC9S08RC8MFJ@LQFP32 [DX3001]	MC9S08RC8MFJE@LQFP32 [DX3001]
MC9S08RC8MP	MC9S08RC8MPE
MC9S08RC8VDW@SOIC28 [DX1033]	MC9S08RC8VDWE@SOIC28 [DX1033]
MC9S08RC8VFD@QFN48 [DX4021]	MC9S08RC8VFDE@QFN48 [DX4021]
MC9S08RC8VFG@LQFP44 [DX3003]	MC9S08RC8VFGE@LQFP44 [DX3003]
MC9S08RC8VFJ@LQFP32 [DX3001]	MC9S08RC8VFJE@LQFP32 [DX3001]
MC9S08RC8VP	MC9S08RC8VPE
MC9S08RD16CDW@SOIC28 [DX1033]	MC9S08RD16CDWE@SOIC28 [DX1033]
MC9S08RD16CFD@QFN48 [DX4021]	MC9S08RD16CFDE@QFN48 [DX4021]
MC9S08RD16CFG@LQFP44 [DX3003]	MC9S08RD16CFGE@LQFP44 [DX3003]
MC9S08RD16CFJ@LQFP32 [DX3001]	MC9S08RD16CFJE@LQFP32 [DX3001]
MC9S08RD16CP	MC9S08RD16CPE
MC9S08RD16MDW@SOIC28 [DX1033]	MC9S08RD16MDWE@SOIC28 [DX1033]
MC9S08RD16MFD@QFN48 [DX4021]	MC9S08RD16MFDE@QFN48 [DX4021]
MC9S08RD16MFG@LQFP44 [DX3003]	MC9S08RD16MFGE@LQFP44 [DX3003]
MC9S08RD16MFJ@LQFP32 [DX3001]	MC9S08RD16MFJE@LQFP32 [DX3001]
MC9S08RD16MP	MC9S08RD16MPE
MC9S08RD16VDW@SOIC28 [DX1033]	MC9S08RD16VDWE@SOIC28 [DX1033]
MC9S08RD16VFD@QFN48 [DX4021]	MC9S08RD16VFDE@QFN48 [DX4021]
MC9S08RD16VFG@LQFP44 [DX3003]	MC9S08RD16VFGE@LQFP44 [DX3003]
MC9S08RD16VFJ@LQFP32 [DX3001]	MC9S08RD16VFJE@LQFP32 [DX3001]
MC9S08RD16VP	MC9S08RD16VPE
MC9S08RD32CDW@SOIC28 [DX1033]	MC9S08RD32CDWE@SOIC28 [DX1033]
MC9S08RD32CFD@QFN48 [DX4021]	MC9S08RD32CFDE@QFN48 [DX4021]
MC9S08RD32CFG@LQFP44 [DX3003]	MC9S08RD32CFGE@LQFP44 [DX3003]
MC9S08RD32CFJ@LQFP32 [DX3001]	MC9S08RD32CFJE@LQFP32 [DX3001]
MC9S08RD32CP	MC9S08RD32CPE
MC9S08RD32MDW@SOIC28 [DX1033]	MC9S08RD32MDWE@SOIC28 [DX1033]
MC9S08RD32MFD@QFN48 [DX4021]	MC9S08RD32MFDE@QFN48 [DX4021]
MC9S08RD32MFG@LQFP44 [DX3003]	MC9S08RD32MFGE@LQFP44 [DX3003]
MC9S08RD32MFJ@LQFP32 [DX3001]	MC9S08RD32MFJE@LQFP32 [DX3001]
MC9S08RD32MP	MC9S08RD32MPE

MC9S08RD32VDW@SOIC28 [DX1033]	MC9S08RD32VDWE@SOIC28 [DX1033]
MC9S08RD32VFD@QFN48 [DX4021]	MC9S08RD32VFDE@QFN48 [DX4021]
MC9S08RD32VFG@LQFP44 [DX3003]	MC9S08RD32VFGE@LQFP44 [DX3003]
MC9S08RD32VFJ@LQFP32 [DX3001]	MC9S08RD32VFJE@LQFP32 [DX3001]
MC9S08RD32VP	MC9S08RD32VPE
MC9S08RD60CDW@SOIC28 [DX1033]	MC9S08RD60CDWE@SOIC28 [DX1033]
MC9S08RD60CFD@QFN48 [DX4021]	MC9S08RD60CFDE@QFN48 [DX4021]
MC9S08RD60CFG@LQFP44 [DX3003]	MC9S08RD60CFGE@LQFP44 [DX3003]
MC9S08RD60CFJ@LQFP32 [DX3001]	MC9S08RD60CFJE@LQFP32 [DX3001]
MC9S08RD60CP	MC9S08RD60CPE
MC9S08RD60MDW@SOIC28 [DX1033]	MC9S08RD60MDWE@SOIC28 [DX1033]
MC9S08RD60MFD@QFN48 [DX4021]	MC9S08RD60MFDE@QFN48 [DX4021]
MC9S08RD60MFG@LQFP44 [DX3003]	MC9S08RD60MFGE@LQFP44 [DX3003]
MC9S08RD60MFJ@LQFP32 [DX3001]	MC9S08RD60MFJE@LQFP32 [DX3001]
MC9S08RD60MP	MC9S08RD60MPE
MC9S08RD60VDW@SOIC28 [DX1033]	MC9S08RD60VDWE@SOIC28 [DX1033]
MC9S08RD60VFD@QFN48 [DX4021]	MC9S08RD60VFDE@QFN48 [DX4021]
MC9S08RD60VFG@LQFP44 [DX3003]	MC9S08RD60VFGE@LQFP44 [DX3003]
MC9S08RD60VFJ@LQFP32 [DX3001]	MC9S08RD60VFJE@LQFP32 [DX3001]
MC9S08RD60VP	MC9S08RD60VPE
MC9S08RD8CDW@SOIC28 [DX1033]	MC9S08RD8CDWE@SOIC28 [DX1033]
MC9S08RD8CFD@QFN48 [DX4021]	MC9S08RD8CFDE@QFN48 [DX4021]
MC9S08RD8CFG@LQFP44 [DX3003]	MC9S08RD8CFGE@LQFP44 [DX3003]
MC9S08RD8CFJ@LQFP32 [DX3001]	MC9S08RD8CFJE@LQFP32 [DX3001]
MC9S08RD8CP	MC9S08RD8CPE
MC9S08RD8MDW@SOIC28 [DX1033]	MC9S08RD8MDWE@SOIC28 [DX1033]
MC9S08RD8MFD@QFN48 [DX4021]	MC9S08RD8MFDE@QFN48 [DX4021]
MC9S08RD8MFG@LQFP44 [DX3003]	MC9S08RD8MFGE@LQFP44 [DX3003]
MC9S08RD8MFJ@LQFP32 [DX3001]	MC9S08RD8MFJE@LQFP32 [DX3001]
MC9S08RD8MP	MC9S08RD8MPE
MC9S08RD8VDW@SOIC28 [DX1033]	MC9S08RD8VDWE@SOIC28 [DX1033]
MC9S08RD8VFD@QFN48 [DX4021]	MC9S08RD8VFDE@QFN48 [DX4021]
MC9S08RD8VFG@LQFP44 [DX3003]	MC9S08RD8VFGE@LQFP44 [DX3003]
MC9S08RD8VFJ@LQFP32 [DX3001]	MC9S08RD8VFJE@LQFP32 [DX3001]
MC9S08RD8VP	MC9S08RD8VPE
MC9S08RE16CDW@SOIC28 [DX1033]	MC9S08RE16CDWE@SOIC28 [DX1033]
MC9S08RE16CFD@QFN48 [DX4021]	MC9S08RE16CFDE@QFN48 [DX4021]
MC9S08RE16CFG@LQFP44 [DX3003]	MC9S08RE16CFGE@LQFP44 [DX3003]
MC9S08RE16CFJ@LQFP32 [DX3001]	MC9S08RE16CFJE@LQFP32 [DX3001]
MC9S08RE16CP	MC9S08RE16CPE
MC9S08RE16MDW@SOIC28 [DX1033]	MC9S08RE16MDWE@SOIC28 [DX1033]
MC9S08RE16MFD@QFN48 [DX4021]	MC9S08RE16MFDE@QFN48 [DX4021]
MC9S08RE16MFG@LQFP44 [DX3003]	MC9S08RE16MFGE@LQFP44 [DX3003]
MC9S08RE16MFJ@LQFP32 [DX3001]	MC9S08RE16MFJE@LQFP32 [DX3001]
MC9S08RE16MP	MC9S08RE16MPE
MC9S08RE16VDW@SOIC28 [DX1033]	MC9S08RE16VDWE@SOIC28 [DX1033]
MC9S08RE16VFD@QFN48 [DX4021]	MC9S08RE16VFDE@QFN48 [DX4021]
MC9S08RE16VFG@LQFP44 [DX3003]	MC9S08RE16VFGE@LQFP44 [DX3003]

MC9S08RE16VFJ@LQFP32 [DX3001]	MC9S08RE16VFJE@LQFP32 [DX3001]
MC9S08RE16VP	MC9S08RE16VPE
MC9S08RE32CDW@SOIC28 [DX1033]	MC9S08RE32CDWE@SOIC28 [DX1033]
MC9S08RE32CFD@QFN48 [DX4021]	MC9S08RE32CFDE@QFN48 [DX4021]
MC9S08RE32CFG@LQFP44 [DX3003]	MC9S08RE32CFGE@LQFP44 [DX3003]
MC9S08RE32CFJ@LQFP32 [DX3001]	MC9S08RE32CFJE@LQFP32 [DX3001]
MC9S08RE32CP	MC9S08RE32CPE
MC9S08RE32MDW@SOIC28 [DX1033]	MC9S08RE32MDWE@SOIC28 [DX1033]
MC9S08RE32MFD@QFN48 [DX4021]	MC9S08RE32MFDE@QFN48 [DX4021]
MC9S08RE32MFG@LQFP44 [DX3003]	MC9S08RE32MFGE@LQFP44 [DX3003]
MC9S08RE32MFJ@LQFP32 [DX3001]	MC9S08RE32MFJE@LQFP32 [DX3001]
MC9S08RE32MP	MC9S08RE32MPE
MC9S08RE32VDW@SOIC28 [DX1033]	MC9S08RE32VDWE@SOIC28 [DX1033]
MC9S08RE32VFD@QFN48 [DX4021]	MC9S08RE32VFDE@QFN48 [DX4021]
MC9S08RE32VFG@LQFP44 [DX3003]	MC9S08RE32VFGE@LQFP44 [DX3003]
MC9S08RE32VFJ@LQFP32 [DX3001]	MC9S08RE32VFJE@LQFP32 [DX3001]
MC9S08RE32VP	MC9S08RE32VPE
MC9S08RE60CDW@SOIC28 [DX1033]	MC9S08RE60CDWE@SOIC28 [DX1033]
MC9S08RE60CFD@QFN48 [DX4021]	MC9S08RE60CFDE@QFN48 [DX4021]
MC9S08RE60CFG@LQFP44 [DX3003]	MC9S08RE60CFGE@LQFP44 [DX3003]
MC9S08RE60CFJ@LQFP32 [DX3001]	MC9S08RE60CFJE@LQFP32 [DX3001]
MC9S08RE60CP	MC9S08RE60CPE
MC9S08RE60MDW@SOIC28 [DX1033]	MC9S08RE60MDWE@SOIC28 [DX1033]
MC9S08RE60MFD@QFN48 [DX4021]	MC9S08RE60MFDE@QFN48 [DX4021]
MC9S08RE60MFG@LQFP44 [DX3003]	MC9S08RE60MFGE@LQFP44 [DX3003]
MC9S08RE60MFJ@LQFP32 [DX3001]	MC9S08RE60MFJE@LQFP32 [DX3001]
MC9S08RE60MP	MC9S08RE60MPE
MC9S08RE60VDW@SOIC28 [DX1033]	MC9S08RE60VDWE@SOIC28 [DX1033]
MC9S08RE60VFD@QFN48 [DX4021]	MC9S08RE60VFDE@QFN48 [DX4021]
MC9S08RE60VFG@LQFP44 [DX3003]	MC9S08RE60VFGE@LQFP44 [DX3003]
MC9S08RE60VFJ@LQFP32 [DX3001]	MC9S08RE60VFJE@LQFP32 [DX3001]
MC9S08RE60VP	MC9S08RE60VPE
MC9S08RE8CDW@SOIC28 [DX1033]	MC9S08RE8CDWE@SOIC28 [DX1033]
MC9S08RE8CFD@QFN48 [DX4021]	MC9S08RE8CFDE@QFN48 [DX4021]
MC9S08RE8CFG@LQFP44 [DX3003]	MC9S08RE8CFGE@LQFP44 [DX3003]
MC9S08RE8CFJ@LQFP32 [DX3001]	MC9S08RE8CFJE@LQFP32 [DX3001]
MC9S08RE8CP	MC9S08RE8CPE
MC9S08RE8MDW@SOIC28 [DX1033]	MC9S08RE8MDWE@SOIC28 [DX1033]
MC9S08RE8MFD@QFN48 [DX4021]	MC9S08RE8MFDE@QFN48 [DX4021]
MC9S08RE8MFG@LQFP44 [DX3003]	MC9S08RE8MFGE@LQFP44 [DX3003]
MC9S08RE8MFJ@LQFP32 [DX3001]	MC9S08RE8MFJE@LQFP32 [DX3001]
MC9S08RE8MP	MC9S08RE8MPE
MC9S08RE8VDW@SOIC28 [DX1033]	MC9S08RE8VDWE@SOIC28 [DX1033]
MC9S08RE8VFD@QFN48 [DX4021]	MC9S08RE8VFDE@QFN48 [DX4021]
MC9S08RE8VFG@LQFP44 [DX3003]	MC9S08RE8VFGE@LQFP44 [DX3003]
MC9S08RE8VFJ@LQFP32 [DX3001]	MC9S08RE8VFJE@LQFP32 [DX3001]
MC9S08RE8VP	MC9S08RE8VPE
MC9S08RG16CDW@SOIC28 [DX1033]	MC9S08RG16CDWE@SOIC28 [DX1033]

MC9S08RG16CFD@QFN48 [DX4021]	MC9S08RG16CFDE@QFN48 [DX4021]
MC9S08RG16CFG@LQFP44 [DX3003]	MC9S08RG16CFGE@LQFP44 [DX3003]
MC9S08RG16CFJ@LQFP32 [DX3001]	MC9S08RG16CFJE@LQFP32 [DX3001]
MC9S08RG16CP	MC9S08RG16CPE
MC9S08RG16MDW@SOIC28 [DX1033]	MC9S08RG16MDWE@SOIC28 [DX1033]
MC9S08RG16MFD@QFN48 [DX4021]	MC9S08RG16MFDE@QFN48 [DX4021]
MC9S08RG16MFG@LQFP44 [DX3003]	MC9S08RG16MFGE@LQFP44 [DX3003]
MC9S08RG16MFJ@LQFP32 [DX3001]	MC9S08RG16MFJE@LQFP32 [DX3001]
MC9S08RG16MP	MC9S08RG16MPE
MC9S08RG16VDW@SOIC28 [DX1033]	MC9S08RG16VDWE@SOIC28 [DX1033]
MC9S08RG16VFD@QFN48 [DX4021]	MC9S08RG16VFDE@QFN48 [DX4021]
MC9S08RG16VFG@LQFP44 [DX3003]	MC9S08RG16VFGE@LQFP44 [DX3003]
MC9S08RG16VFJ@LQFP32 [DX3001]	MC9S08RG16VFJE@LQFP32 [DX3001]
MC9S08RG16VP	MC9S08RG16VPE
MC9S08RG32CDW@SOIC28 [DX1033]	MC9S08RG32CDWE@SOIC28 [DX1033]
MC9S08RG32CFD@QFN48 [DX4021]	MC9S08RG32CFDE@QFN48 [DX4021]
MC9S08RG32CFG@LQFP44 [DX3003]	MC9S08RG32CFGE@LQFP44 [DX3003]
MC9S08RG32CFJ@LQFP32 [DX3001]	MC9S08RG32CFJE@LQFP32 [DX3001]
MC9S08RG32CP	MC9S08RG32CPE
MC9S08RG32MDW@SOIC28 [DX1033]	MC9S08RG32MDWE@SOIC28 [DX1033]
MC9S08RG32MFD@QFN48 [DX4021]	MC9S08RG32MFDE@QFN48 [DX4021]
MC9S08RG32MFG@LQFP44 [DX3003]	MC9S08RG32MFGE@LQFP44 [DX3003]
MC9S08RG32MFJ@LQFP32 [DX3001]	MC9S08RG32MFJE@LQFP32 [DX3001]
MC9S08RG32MP	MC9S08RG32MPE
MC9S08RG32VDW@SOIC28 [DX1033]	MC9S08RG32VDWE@SOIC28 [DX1033]
MC9S08RG32VFD@QFN48 [DX4021]	MC9S08RG32VFDE@QFN48 [DX4021]
MC9S08RG32VFG@LQFP44 [DX3003]	MC9S08RG32VFGE@LQFP44 [DX3003]
MC9S08RG32VFJ@LQFP32 [DX3001]	MC9S08RG32VFJE@LQFP32 [DX3001]
MC9S08RG32VP	MC9S08RG32VPE
MC9S08RG60CDW@SOIC28 [DX1033]	MC9S08RG60CDWE@SOIC28 [DX1033]
MC9S08RG60CFD@QFN48 [DX4021]	MC9S08RG60CFDE@QFN48 [DX4021]
MC9S08RG60CFG@LQFP44 [DX3003]	MC9S08RG60CFGE@LQFP44 [DX3003]
MC9S08RG60CFJ@LQFP32 [DX3001]	MC9S08RG60CFJE@LQFP32 [DX3001]
MC9S08RG60CP	MC9S08RG60CPE
MC9S08RG60MDW@SOIC28 [DX1033]	MC9S08RG60MDWE@SOIC28 [DX1033]
MC9S08RG60MFD@QFN48 [DX4021]	MC9S08RG60MFDE@QFN48 [DX4021]
MC9S08RG60MFG@LQFP44 [DX3003]	MC9S08RG60MFGE@LQFP44 [DX3003]
MC9S08RG60MFJ@LQFP32 [DX3001]	MC9S08RG60MFJE@LQFP32 [DX3001]
MC9S08RG60MP	MC9S08RG60MPE
MC9S08RG60VDW@SOIC28 [DX1033]	MC9S08RG60VDWE@SOIC28 [DX1033]
MC9S08RG60VFD@QFN48 [DX4021]	MC9S08RG60VFDE@QFN48 [DX4021]
MC9S08RG60VFG@LQFP44 [DX3003]	MC9S08RG60VFGE@LQFP44 [DX3003]
MC9S08RG60VFJ@LQFP32 [DX3001]	MC9S08RG60VFJE@LQFP32 [DX3001]
MC9S08RG60VP	MC9S08RG60VPE
MC9S08RG8CDW@SOIC28 [DX1033]	MC9S08RG8CDWE@SOIC28 [DX1033]
MC9S08RG8CFD@QFN48 [DX4021]	MC9S08RG8CFDE@QFN48 [DX4021]
MC9S08RG8CFG@LQFP44 [DX3003]	MC9S08RG8CFGE@LQFP44 [DX3003]
MC9S08RG8CFJ@LQFP32 [DX3001]	MC9S08RG8CFJE@LQFP32 [DX3001]

MC9S08RG8CP
MC9S08RG8CPE
MC9S08RG8MDW@SOIC28 [DX1033]
MC9S08RG8MDWE@SOIC28 [DX1033]
MC9S08RG8MFD@QFN48 [DX4021]
MC9S08RG8MFDE@QFN48 [DX4021]
MC9S08RG8MFG@LQFP44 [DX3003]
MC9S08RG8MFGE@LQFP44 [DX3003]
MC9S08RG8MFJ@LQFP32 [DX3001]
MC9S08RG8MFJE@LQFP32 [DX3001]
MC9S08RG8MP
MC9S08RG8MPE
MC9S08RG8VDW@SOIC28 [DX1033]
MC9S08RG8VDWE@SOIC28 [DX1033]
MC9S08RG8VFD@QFN48 [DX4021]
MC9S08RG8VFDE@QFN48 [DX4021]
MC9S08RG8VFG@LQFP44 [DX3003]
MC9S08RG8VFGE@LQFP44 [DX3003]
MC9S08RG8VFJ@LQFP32 [DX3001]
MC9S08RG8VFJE@LQFP32 [DX3001]
MC9S08RG8VP
MC9S08RG8VPE
MC9S08SE4CRL [DX0001]
MC9S08SE4CTG [DX1001]
MC9S08SE4CWL [DX1033]
MC9S08SE4MRL [DX0001]
MC9S08SE4MTG [DX1001]
MC9S08SE4MWL [DX1033]
MC9S08SE4VRL [DX0001]
MC9S08SE4VTG [DX1001]
MC9S08SE4VWL [DX1033]
MC9S08SE8CRL [DX0001]
MC9S08SE8CTG [DX1001]
MC9S08SE8CWL [DX1033]
MC9S08SE8MRL [DX0001]
MC9S08SE8MTG [DX1001]
MC9S08SE8MWL [DX1033]
MC9S08SE8VRL [DX0001]
MC9S08SE8VTG [DX1001]
MC9S08SE8VWL [DX1033]
MC9S08SG16CTG@TSSOP16 [DX1000]
MC9S08SG16CTGE@TSSOP16 [DX1000]
MC9S08SG16CTJ@TSSOP20 [DX1000]
MC9S08SG16CTJE@TSSOP20 [DX1000]
MC9S08SG16CTL@TSSOP28 [DX1001]
MC9S08SG16CTLE@TSSOP28 [DX1001]
MC9S08SG16MTG@TSSOP16 [DX1000]
MC9S08SG16MTGE@TSSOP16 [DX1000]
MC9S08SG16MTJ@TSSOP20 [DX1000]
MC9S08SG16MTJE@TSSOP20 [DX1000]
MC9S08SG16MTL@TSSOP28 [DX1001]
MC9S08SG16MTLE@TSSOP28 [DX1001]
MC9S08SG16VTG@TSSOP16 [DX1000]
MC9S08SG16VTGE@TSSOP16 [DX1000]
MC9S08SG16VTJ@TSSOP20 [DX1000]
MC9S08SG16VTJE@TSSOP20 [DX1000]
MC9S08SG16VTL@TSSOP28 [DX1001]
MC9S08SG16VTLE@TSSOP28 [DX1001]
MC9S08SG32CTG@TSSOP16 [DX1000]
MC9S08SG32CTGE@TSSOP16 [DX1000]
MC9S08SG32CTJ@TSSOP20 [DX1000]
MC9S08SG32CTJE@TSSOP20 [DX1000]
MC9S08SG32CTL@TSSOP28 [DX1001]
MC9S08SG32CTLE@TSSOP28 [DX1001]
MC9S08SG32MTG@TSSOP16 [DX1000]
MC9S08SG32MTGE@TSSOP16 [DX1000]
MC9S08SG32MTJ@TSSOP20 [DX1000]
MC9S08SG32MTJE@TSSOP20 [DX1000]
MC9S08SG32MTL@TSSOP28 [DX1001]
MC9S08SG32MTLE@TSSOP28 [DX1001]
MC9S08SG32VTG@TSSOP16 [DX1000]
MC9S08SG32VTGE@TSSOP16 [DX1000]
MC9S08SG32VTJ@TSSOP20 [DX1000]
MC9S08SG32VTJE@TSSOP20 [DX1000]
MC9S08SG32VTL@TSSOP28 [DX1001]
MC9S08SG32VTLE@TSSOP28 [DX1001]
MC9S08SG4CSC@SOIC8 [DX1030]
MC9S08SG4CSCE@SOIC8 [DX1030]
MC9S08SG4CTG@TSSOP16 [DX1000]
MC9S08SG4CTGE@TSSOP16 [DX1000]
MC9S08SG4CTJ@TSSOP20 [DX1000]
MC9S08SG4CTJE@TSSOP20 [DX1000]
MC9S08SG4MSC@SOIC8 [DX1030]
MC9S08SG4MSCE@SOIC8 [DX1030]
MC9S08SG4MTG@TSSOP16 [DX1000]
MC9S08SG4MTGE@TSSOP16 [DX1000]
MC9S08SG4MTJ@TSSOP20 [DX1000]
MC9S08SG4MTJE@TSSOP20 [DX1000]
MC9S08SG4VSC@SOIC8 [DX1030]
MC9S08SG4VSCE@SOIC8 [DX1030]
MC9S08SG4VTG@TSSOP16 [DX1000]
MC9S08SG4VTGE@TSSOP16 [DX1000]
MC9S08SG4VTJ@TSSOP20 [DX1000]
MC9S08SG4VTJE@TSSOP20 [DX1000]
MC9S08SG8CSC@SOIC8 [DX1030]
MC9S08SG8CSCE@SOIC8 [DX1030]

MC9S08SG8CTG@TSSOP16 [DX1000]
MC9S08SG8CTGE@TSSOP16 [DX1000]
MC9S08SG8CTJ@TSSOP20 [DX1000]
MC9S08SG8CTJE@TSSOP20 [DX1000]
MC9S08SG8MSC@SOIC8 [DX1030]
MC9S08SG8MSCE@SOIC8 [DX1030]
MC9S08SG8MTG@TSSOP16 [DX1000]
MC9S08SG8MTGE@TSSOP16 [DX1000]
MC9S08SG8MTJ@TSSOP20 [DX1000]
MC9S08SG8MTJE@TSSOP20 [DX1000]
MC9S08SG8VSC@SOIC8 [DX1030]
MC9S08SG8VSCE@SOIC8 [DX1030]
MC9S08SG8VTG@TSSOP16 [DX1000]
MC9S08SG8VTGE@TSSOP16 [DX1000]
MC9S08SG8VTJ@TSSOP20 [DX1000]
MC9S08SG8VTJE@TSSOP20 [DX1000]
MC9S08SH16CTG@TSSOP16 [DX1000]
MC9S08SH16CTGE@TSSOP16 [DX1000]
MC9S08SH16CTJ@TSSOP20 [DX1000]
MC9S08SH16CTJE@TSSOP20 [DX1000]
MC9S08SH16CTL@TSSOP28 [DX1001]
MC9S08SH16CTLE@TSSOP28 [DX1001]
MC9S08SH16CWL@SOIC28 [DX1033]
MC9S08SH16CWLE@SOIC28 [DX1033]
MC9S08SH16MTG@TSSOP16 [DX1000]
MC9S08SH16MTGE@TSSOP16 [DX1000]
MC9S08SH16MTJ@TSSOP20 [DX1000]
MC9S08SH16MTJE@TSSOP20 [DX1000]
MC9S08SH16MTL@TSSOP28 [DX1001]
MC9S08SH16MTLE@TSSOP28 [DX1001]
MC9S08SH16MWL@SOIC28 [DX1033]
MC9S08SH16MWLE@SOIC28 [DX1033]
MC9S08SH16VTG@TSSOP16 [DX1000]
MC9S08SH16VTGE@TSSOP16 [DX1000]
MC9S08SH16VTJ@TSSOP20 [DX1000]
MC9S08SH16VTJE@TSSOP20 [DX1000]
MC9S08SH16VTL@TSSOP28 [DX1001]
MC9S08SH16VTLE@TSSOP28 [DX1001]
MC9S08SH16VWL@SOIC28 [DX1033]
MC9S08SH16VWLE@SOIC28 [DX1033]
MC9S08SH32CTG@TSSOP16 [DX1000]
MC9S08SH32CTGE@TSSOP16 [DX1000]
MC9S08SH32CTJ@TSSOP20 [DX1000]
MC9S08SH32CTJE@TSSOP20 [DX1000]
MC9S08SH32CTL@TSSOP28 [DX1001]
MC9S08SH32CTLE@TSSOP28 [DX1001]
MC9S08SH32CWL@SOIC28 [DX1033]
MC9S08SH32CWLE@SOIC28 [DX1033]
MC9S08SH32MTG@TSSOP16 [DX1000]
MC9S08SH32MTGE@TSSOP16 [DX1000]
MC9S08SH32MTJ@TSSOP20 [DX1000]
MC9S08SH32MTJE@TSSOP20 [DX1000]
MC9S08SH32MTL@TSSOP28 [DX1001]
MC9S08SH32MTLE@TSSOP28 [DX1001]
MC9S08SH32MWL@SOIC28 [DX1033]
MC9S08SH32MWLE@SOIC28 [DX1033]
MC9S08SH32VTG@TSSOP16 [DX1000]
MC9S08SH32VTGE@TSSOP16 [DX1000]
MC9S08SH32VTJ@TSSOP20 [DX1000]
MC9S08SH32VTJE@TSSOP20 [DX1000]
MC9S08SH32VTL@TSSOP28 [DX1001]
MC9S08SH32VTLE@TSSOP28 [DX1001]
MC9S08SH32VWL@SOIC28 [DX1033]
MC9S08SH32VWLE@SOIC28 [DX1033]
MC9S08SH4CFK@QFN24 [DX4012]
MC9S08SH4CFK@QFN24(auto trim) [DX4012]
MC9S08SH4CFKE@QFN24 [DX4012]
MC9S08SH4CFKE@QFN24(auto trim) [DX4012]
MC9S08SH4CPJ
MC9S08SH4CPJ(auto trim)
MC9S08SH4CPJE
MC9S08SH4CPJE(auto trim)
MC9S08SH4CSC@SOIC8 [DX1030]
MC9S08SH4CSC@SOIC8(auto trim) [DX1030]
MC9S08SH4CSCE@SOIC8 [DX1030]
MC9S08SH4CSCE@SOIC8(auto trim) [DX1030]
MC9S08SH4CTG@TSSOP16 [DX1000]
MC9S08SH4CTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4CTGE@TSSOP16 [DX1000]
MC9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4CTJ@TSSOP20 [DX1000]
MC9S08SH4CTJ@TSSOP20(auto trim) [DX1000]

MC9S08SH4CTJE@TSSOP20 [DX1000]
MC9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4CWJ@SOIC20 [DX1033]
MC9S08SH4CWJ@SOIC20(auto trim) [DX1033]
MC9S08SH4CWJE@SOIC20 [DX1033]
MC9S08SH4CWJE@SOIC20(auto trim) [DX1033]
MC9S08SH4MFK@QFN24 [DX4012]
MC9S08SH4MFK@QFN24(auto trim) [DX4012]
MC9S08SH4MFKE@QFN24 [DX4012]
MC9S08SH4MFKE@QFN24(auto trim) [DX4012]
MC9S08SH4MPJ MC9S08SH4MPJ(auto trim)
MC9S08SH4MPJE MC9S08SH4MPJE(auto trim)
MC9S08SH4MSC@SOIC8 [DX1030]
MC9S08SH4MSC@SOIC8(auto trim) [DX1030]
MC9S08SH4MSCE@SOIC8 [DX1030]
MC9S08SH4MSCE@SOIC8(auto trim) [DX1030]
MC9S08SH4MTG@TSSOP16 [DX1000]
MC9S08SH4MTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4MTGE@TSSOP16 [DX1000]
MC9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4MTJ@TSSOP20 [DX1000]
MC9S08SH4MTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH4MTJE@TSSOP20 [DX1000]
MC9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4MWJ@SOIC20 [DX1033]
MC9S08SH4MWJ@SOIC20(auto trim) [DX1033]
MC9S08SH4MWJE@SOIC20 [DX1033]
MC9S08SH4MWJE@SOIC20(auto trim) [DX1033]
MC9S08SH4VFK@QFN24 [DX4012]
MC9S08SH4VFK@QFN24(auto trim) [DX4012]
MC9S08SH4VFKE@QFN24 [DX4012]
MC9S08SH4VFKE@QFN24(auto trim) [DX4012]
MC9S08SH4VPJ MC9S08SH4VPJ(auto trim)
MC9S08SH4VPJE MC9S08SH4VPJE(auto trim)
MC9S08SH4VSC@SOIC8 [DX1030]
MC9S08SH4VSC@SOIC8(auto trim) [DX1030]
MC9S08SH4VSCE@SOIC8 [DX1030]
MC9S08SH4VSCE@SOIC8(auto trim) [DX1030]
MC9S08SH4VTG@TSSOP16 [DX1000]
MC9S08SH4VTG@TSSOP16(auto trim) [DX1000]
MC9S08SH4VTGE@TSSOP16 [DX1000]
MC9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH4VTJ@TSSOP20 [DX1000]
MC9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH4VTJE@TSSOP20 [DX1000]
MC9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH4VWJ@SOIC20 [DX1033]
MC9S08SH4VWJ@SOIC20(auto trim) [DX1033]

MC9S08SH4VWJE@SOIC20 [DX1033]
MC9S08SH4VWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8CFK@QFN24 [DX4012]
MC9S08SH8CFK@QFN24(auto trim) [DX4012]
MC9S08SH8CFKE@QFN24 [DX4012]
MC9S08SH8CFKE@QFN24(auto trim) [DX4012]
MC9S08SH8CPJ MC9S08SH8CPJ(auto trim)
MC9S08SH8CPJE MC9S08SH8CPJE(auto trim)
MC9S08SH8CSC@SOIC8 [DX1030]
MC9S08SH8CSC@SOIC8(auto trim) [DX1030]
MC9S08SH8CSCE@SOIC8 [DX1030]
MC9S08SH8CSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8CTG@TSSOP16 [DX1000]
MC9S08SH8CTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8CTGE@TSSOP16 [DX1000]
MC9S08SH8CTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH8CTJ@TSSOP20 [DX1000]
MC9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8CTJE@TSSOP20 [DX1000]
MC9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH8CWJ@SOIC20 [DX1033]
MC9S08SH8CWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8CWJE@SOIC20 [DX1033]
MC9S08SH8CWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8MFK@QFN24 [DX4012]
MC9S08SH8MFK@QFN24(auto trim) [DX4012]
MC9S08SH8MFKE@QFN24 [DX4012]
MC9S08SH8MFKE@QFN24(auto trim) [DX4012]
MC9S08SH8MPJ MC9S08SH8MPJ(auto trim)
MC9S08SH8MPJE MC9S08SH8MPJE(auto trim)
MC9S08SH8MSC@SOIC8 [DX1030]
MC9S08SH8MSC@SOIC8(auto trim) [DX1030]
MC9S08SH8MSCE@SOIC8 [DX1030]
MC9S08SH8MSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8MTG@TSSOP16 [DX1000]
MC9S08SH8MTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8MTGE@TSSOP16 [DX1000]
MC9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH8MTJ@TSSOP20 [DX1000]
MC9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8MTJE@TSSOP20 [DX1000]
MC9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH8MWJ@SOIC20 [DX1033]
MC9S08SH8MWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8MWJE@SOIC20 [DX1033]
MC9S08SH8MWJE@SOIC20(auto trim) [DX1033]
MC9S08SH8VFK@QFN24 [DX4012]
MC9S08SH8VFK@QFN24(auto trim) [DX4012]

MC9S08SH8VFKE@QFN24 [DX4012]
MC9S08SH8VFKE@QFN24(auto trim) [DX4012]
MC9S08SH8VPJ MC9S08SH8VPJ(auto trim)
MC9S08SH8VPJE MC9S08SH8VPJE(auto trim)
MC9S08SH8VSC@SOIC8 [DX1030]
MC9S08SH8VSC@SOIC8(auto trim) [DX1030]
MC9S08SH8VSCE@SOIC8 [DX1030]
MC9S08SH8VSCE@SOIC8(auto trim) [DX1030]
MC9S08SH8VTG@TSSOP16 [DX1000]
MC9S08SH8VTG@TSSOP16(auto trim) [DX1000]
MC9S08SH8VTGE@TSSOP16 [DX1000]
MC9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
MC9S08SH8VTJ@TSSOP20 [DX1000]
MC9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
MC9S08SH8VTJE@TSSOP20 [DX1000]
MC9S08SH8VTJE@TSSOP20(auto trim) [DX1000]
MC9S08SH8VWJ@SOIC20 [DX1033]
MC9S08SH8VWJ@SOIC20(auto trim) [DX1033]
MC9S08SH8VWJE@SOIC20 [DX1033]
MC9S08SH8VWJE@SOIC20(auto trim) [DX1033]
MC9S08SL16CTJ@TSSOP20 [DX1000] MC9S08SL16CTJE@TSSOP20 [DX1000]
MC9S08SL16CTL@TSSOP28 [DX1001] MC9S08SL16CTLE@TSSOP28 [DX1001]
MC9S08SL16MTJ@TSSOP20 [DX1000] MC9S08SL16MTJE@TSSOP20 [DX1000]
MC9S08SL16MTL@TSSOP28 [DX1001] MC9S08SL16MTLE@TSSOP28 [DX1001]
MC9S08SL16VTJ@TSSOP20 [DX1000] MC9S08SL16VTJE@TSSOP20 [DX1000]
MC9S08SL16VTL@TSSOP28 [DX1001] MC9S08SL16VTLE@TSSOP28 [DX1001]
MC9S08SL8CTJ@TSSOP20 [DX1000] MC9S08SL8CTJE@TSSOP20 [DX1000]
MC9S08SL8CTL@TSSOP28 [DX1001] MC9S08SL8CTLE@TSSOP28 [DX1001]
MC9S08SL8MTJ@TSSOP20 [DX1000] MC9S08SL8MTJE@TSSOP20 [DX1000]
MC9S08SL8MTL@TSSOP28 [DX1001] MC9S08SL8MTLE@TSSOP28 [DX1001]
MC9S08SL8VTJ@TSSOP20 [DX1000] MC9S08SL8VTJE@TSSOP20 [DX1000]
MC9S08SL8VTL@TSSOP28 [DX1001] MC9S08SL8VTLE@TSSOP28 [DX1001]
MC9S08SV16CBM@SDIP32 [DX0032] MC9S08SV16CLC@LQFP32 [DX3001]
MC9S08SV16MBM@SDIP32 [DX0032] MC9S08SV16MLC@LQFP32 [DX3001]
MC9S08SV16VBM@SDIP32 [DX0032] MC9S08SV16VLC@LQFP32 [DX3001]
MC9S08SV8CBM@SDIP32 [DX0032] MC9S08SV8CLC@LQFP32 [DX3001]
MC9S08SV8MBM@SDIP32 [DX0032] MC9S08SV8MLC@LQFP32 [DX3001]
MC9S08SV8VBM@SDIP32 [DX0032] MC9S08SV8VLC@LQFP32 [DX3001]
MC9S12A128BCFU@TQFP80 [DX3018] MC9S12A128BCPV@TQFP112 [DX3026]
MC9S12A128BMFU@TQFP80 [DX3018] MC9S12A128BMPV@TQFP112 [DX3026]
MC9S12A128BVFU@TQFP80 [DX3018] MC9S12A128BVPV@TQFP112 [DX3026]
MC9S12A128CFU@TQFP80 [DX3018] MC9S12A128CPV@TQFP112 [DX3026]
MC9S12A128MFU@TQFP80 [DX3018] MC9S12A128MPV@TQFP112 [DX3026]
MC9S12A128VFU@TQFP80 [DX3018] MC9S12A128VPV@TQFP112 [DX3026]
MC9S12A256BCFU@TQFP80 [DX3018] MC9S12A256BCPV@TQFP112 [DX3026]
MC9S12A256BMFU@TQFP80 [DX3018] MC9S12A256BMPV@TQFP112 [DX3026]
MC9S12A256BVFU@TQFP80 [DX3018] MC9S12A256BVPV@TQFP112 [DX3026]
MC9S12A256CFU@TQFP80 [DX3018] MC9S12A256CPV@TQFP112 [DX3026]

MC9S12A256MFU@TQFP80 [DX3018]
MC9S12A256MPV@TQFP112 [DX3026]
MC9S12A256VFU@TQFP80 [DX3018]
MC9S12A256VPV@TQFP112 [DX3026]
MC9S12A512CPV@TQFP112 [DX3026]
MC9S12A512MPV@TQFP112 [DX3026]
MC9S12A512VPV@TQFP112 [DX3026]
MC9S12A64CFU@TQFP80 [DX3018]
MC9S12A64CPV@TQFP112 [DX3026]
MC9S12A64MFU@TQFP80 [DX3018]
MC9S12A64MPV@TQFP112 [DX3026]
MC9S12A64VFU@TQFP80 [DX3018]
MC9S12A64VPV@TQFP112 [DX3026]
MC9S12B128CFU@TQFP80 [DX3018]
MC9S12B128CPV@TQFP112 [DX3026]
MC9S12B128MFU@TQFP80 [DX3018]
MC9S12B128MPV@TQFP112 [DX3026]
MC9S12B128VFU@TQFP80 [DX3018]
MC9S12B128VPV@TQFP112 [DX3026]
MC9S12B256CFU@TQFP80 [DX3018]
MC9S12B256CPV@TQFP112 [DX3026]
MC9S12B256MFU@TQFP80 [DX3018]
MC9S12B256MPV@TQFP112 [DX3026]
MC9S12B256VFU@TQFP80 [DX3018]
MC9S12B256VPV@TQFP112 [DX3026]
MC9S12B64CFU@TQFP80 [DX3018]
MC9S12B64CPV@TQFP112 [DX3026]
MC9S12B64MFU@TQFP80 [DX3018]
MC9S12B64MPV@TQFP112 [DX3026]
MC9S12B64VFU@TQFP80 [DX3018]
MC9S12B64VPV@TQFP112 [DX3026]
MC9S12C128CFA@TQFP48 [DX3007]
MC9S12C128CFU@TQFP80 [DX3018]
MC9S12C128CPB@TQFP52 [DX3010]
MC9S12C128MFA@TQFP48 [DX3007]
MC9S12C128MFU@TQFP80 [DX3018]
MC9S12C128MPB@TQFP52 [DX3010]
MC9S12C128VFA@TQFP48 [DX3007]
MC9S12C128VFU@TQFP80 [DX3018]
MC9S12C128VPB@TQFP52 [DX3010]
MC9S12C32CFA16@TQFP48 [DX3007]
MC9S12C32CFA25@TQFP48 [DX3007]
MC9S12C32CFU16@TQFP80 [DX3018]
MC9S12C32CFU25@TQFP80 [DX3018]
MC9S12C32CPB16@TQFP52 [DX3010]
MC9S12C32CPB25@TQFP52 [DX3010]
MC9S12C32MFA16@TQFP48 [DX3007]
MC9S12C32MFA25@TQFP48 [DX3007]
MC9S12C32MFU16@TQFP80 [DX3018]
MC9S12C32MFU25@TQFP80 [DX3018]
MC9S12C32MPB16@TQFP52 [DX3010]
MC9S12C32MPB25@TQFP52 [DX3010]
MC9S12C32VFA16@TQFP48 [DX3007]
MC9S12C32VFA25@TQFP48 [DX3007]
MC9S12C32VFU16@TQFP80 [DX3018]
MC9S12C32VFU25@TQFP80 [DX3018]
MC9S12C32VPB16@TQFP52 [DX3010]
MC9S12C32VPB25@TQFP52 [DX3010]
MC9S12C64CFA@TQFP48 [DX3007]
MC9S12C64CFU@TQFP80 [DX3018]
MC9S12C64CPB@TQFP52 [DX3010]
MC9S12C64MFA@TQFP48 [DX3007]
MC9S12C64MFU@TQFP80 [DX3018]
MC9S12C64MPB@TQFP52 [DX3010]
MC9S12C64VFA@TQFP48 [DX3007]
MC9S12C64VFU@TQFP80 [DX3018]
MC9S12C64VPB@TQFP52 [DX3010]
MC9S12C96CFA@TQFP48 [DX3007]
MC9S12C96CFU@TQFP80 [DX3018]
MC9S12C96CPB@TQFP52 [DX3010]
MC9S12C96MFA@TQFP48 [DX3007]
MC9S12C96MFU@TQFP80 [DX3018]
MC9S12C96MPB@TQFP52 [DX3010]
MC9S12C96VFA@TQFP48 [DX3007]
MC9S12C96VFU@TQFP80 [DX3018]
MC9S12C96VPB@TQFP52 [DX3010]
MC9S12D32CFU@TQFP80 [DX3018]
MC9S12D32MFU@TQFP80 [DX3018]
MC9S12D32VFU@TQFP80 [DX3018]
MC9S12D64CFU@TQFP80 [DX3018]
MC9S12D64CPV@TQFP112 [DX3026]
MC9S12D64MFU@TQFP80 [DX3018]
MC9S12D64MPV@TQFP112 [DX3026]
MC9S12D64VFU@TQFP80 [DX3018]
MC9S12D64VPV@TQFP112 [DX3026]
MC9S12DB128BCFU@TQFP80 [DX3018]
MC9S12DB128BCPV@TQFP112 [DX3026]
MC9S12DB128BMFU@TQFP80 [DX3018]
MC9S12DB128BMPV@TQFP112 [DX3026]
MC9S12DB128BVFU@TQFP80 [DX3018]
MC9S12DB128BVPV@TQFP112 [DX3026]
MC9S12DB128CFU@TQFP80 [DX3018]
MC9S12DB128CPV@TQFP112 [DX3026]
MC9S12DB128MFU@TQFP80 [DX3018]
MC9S12DB128MPV@TQFP112 [DX3026]
MC9S12DB128VFU@TQFP80 [DX3018]

MC9S12DB128VPV@TQFP112 [DX3026]
MC9S12DG128BCPV@TQFP112 [DX3026]
MC9S12DG128BMPV@TQFP112 [DX3026]
MC9S12DG128BVPV@TQFP112 [DX3026]
MC9S12DG128CPV@TQFP112 [DX3026]
MC9S12DG128ECPV@TQFP112 [DX3026]
MC9S12DG128EMPV@TQFP112 [DX3026]
MC9S12DG128EVPV@TQFP112 [DX3026]
MC9S12DG128MPV@TQFP112 [DX3026]
MC9S12DG128VPV@TQFP112 [DX3026]
MC9S12DG256BCPV@TQFP112 [DX3026]
MC9S12DG256BMPV@TQFP112 [DX3026]
MC9S12DG256BVPV@TQFP112 [DX3026]
MC9S12DG256CCPV@TQFP112 [DX3026]
MC9S12DG256CMFU@TQFP80 [DX3018]
MC9S12DG256CPV@TQFP112 [DX3026]
MC9S12DG256CVPV@TQFP112 [DX3026]
MC9S12DG256MPV@TQFP112 [DX3026]
MC9S12DG256VPV@TQFP112 [DX3026]
MC9S12DJ128BCPV@TQFP112 [DX3026]
MC9S12DJ128BMPV@TQFP112 [DX3026]
MC9S12DJ128BVPV@TQFP112 [DX3026]
MC9S12DJ128CPV@TQFP112 [DX3026]
MC9S12DJ128ECPV@TQFP112 [DX3026]
MC9S12DJ128EMPV@TQFP112 [DX3026]
MC9S12DJ128EVPV@TQFP112 [DX3026]
MC9S12DJ128MPV@TQFP112 [DX3026]
MC9S12DJ128VPV@TQFP112 [DX3026]
MC9S12DJ256BCPV@TQFP112 [DX3026]
MC9S12DJ256BMPV@TQFP112 [DX3026]
MC9S12DJ256BVPV@TQFP112 [DX3026]
MC9S12DJ256CCPV@TQFP112 [DX3026]
MC9S12DJ256CMFU@TQFP80 [DX3018]
MC9S12DJ256CPV@TQFP112 [DX3026]
MC9S12DJ256CVPV@TQFP112 [DX3026]
MC9S12DJ256MPV@TQFP112 [DX3026]
MC9S12DJ256VPV@TQFP112 [DX3026]
MC9S12DJ512MPV@TQFP112 [DX3026]
MC9S12DJ64CFU@TQFP80 [DX3018]
MC9S12DJ64MFU@TQFP80 [DX3018]
MC9S12DJ64VFU@TQFP80 [DX3018]
MC9S12DP256BCFU@TQFP80 [DX3018]
MC9S12DP256BMFU@TQFP80 [DX3018]
MC9S12DP256BVFU@TQFP80 [DX3018]
MC9S12DP256CCFU@TQFP80 [DX3018]
MC9S12DP256CMFU@TQFP80 [DX3018]
MC9S12DP256CVFU@TQFP80 [DX3018]
MC9S12DP512CPV@TQFP112 [DX3026]
MC9S12DG128BCFU@TQFP80 [DX3018]
MC9S12DG128BMFU@TQFP80 [DX3018]
MC9S12DG128BVFU@TQFP80 [DX3018]
MC9S12DG128CFU@TQFP80 [DX3018]
MC9S12DG128ECFU@TQFP80 [DX3018]
MC9S12DG128EMFU@TQFP80 [DX3018]
MC9S12DG128EVFU@TQFP80 [DX3018]
MC9S12DG128MFU@TQFP80 [DX3018]
MC9S12DG128VFU@TQFP80 [DX3018]
MC9S12DG256BCFU@TQFP80 [DX3018]
MC9S12DG256BMFU@TQFP80 [DX3018]
MC9S12DG256BVFU@TQFP80 [DX3018]
MC9S12DG256CCFU@TQFP80 [DX3018]
MC9S12DG256CFU@TQFP80 [DX3018]
MC9S12DG256CMPV@TQFP112 [DX3026]
MC9S12DG256CVFU@TQFP80 [DX3018]
MC9S12DG256MFU@TQFP80 [DX3018]
MC9S12DG256VFU@TQFP80 [DX3018]
MC9S12DJ128BCFU@TQFP80 [DX3018]
MC9S12DJ128BMFU@TQFP80 [DX3018]
MC9S12DJ128BVFU@TQFP80 [DX3018]
MC9S12DJ128CFU@TQFP80 [DX3018]
MC9S12DJ128ECFU@TQFP80 [DX3018]
MC9S12DJ128EMFU@TQFP80 [DX3018]
MC9S12DJ128EVFU@TQFP80 [DX3018]
MC9S12DJ128MFU@TQFP80 [DX3018]
MC9S12DJ128VFU@TQFP80 [DX3018]
MC9S12DJ256BCFU@TQFP80 [DX3018]
MC9S12DJ256BMFU@TQFP80 [DX3018]
MC9S12DJ256BVFU@TQFP80 [DX3018]
MC9S12DJ256CCFU@TQFP80 [DX3018]
MC9S12DJ256CFU@TQFP80 [DX3018]
MC9S12DJ256CMPV@TQFP112 [DX3026]
MC9S12DJ256CVFU@TQFP80 [DX3018]
MC9S12DJ256MFU@TQFP80 [DX3018]
MC9S12DJ256VFU@TQFP80 [DX3018]
MC9S12DJ512CPV@TQFP112 [DX3026]
MC9S12DJ512VPV@TQFP112 [DX3026]
MC9S12DJ64CPV@TQFP112 [DX3026]
MC9S12DJ64MPV@TQFP112 [DX3026]
MC9S12DJ64VPV@TQFP112 [DX3026]
MC9S12DP256BCPV@TQFP112 [DX3026]
MC9S12DP256BMPV@TQFP112 [DX3026]
MC9S12DP256BVPV@TQFP112 [DX3026]
MC9S12DP256CCPV@TQFP112 [DX3026]
MC9S12DP256CMPV@TQFP112 [DX3026]
MC9S12DP256CVPV@TQFP112 [DX3026]
MC9S12DP512MPV@TQFP112 [DX3026]

MC9S12DP512VPV@TQFP112 [DX3026]
MC9S12DT128BCPV@TQFP112 [DX3026]
MC9S12DT128BMPV@TQFP112 [DX3026]
MC9S12DT128BVPV@TQFP112 [DX3026]
MC9S12DT128CPV@TQFP112 [DX3026]
MC9S12DT128ECPV@TQFP112 [DX3026]
MC9S12DT128EMPV@TQFP112 [DX3026]
MC9S12DT128EVPV@TQFP112 [DX3026]
MC9S12DT128MPV@TQFP112 [DX3026]
MC9S12DT128VPV@TQFP112 [DX3026]
MC9S12DT256BCPV@TQFP112 [DX3026]
MC9S12DT256BMPV@TQFP112 [DX3026]
MC9S12DT256BVPV@TQFP112 [DX3026]
MC9S12DT256CCPV@TQFP112 [DX3026]
MC9S12DT256CMFU@TQFP80 [DX3018]
MC9S12DT256CPV@TQFP112 [DX3026]
MC9S12DT256CVPV@TQFP112 [DX3026]
MC9S12DT256MPV@TQFP112 [DX3026]
MC9S12DT256VPV@TQFP112 [DX3026]
MC9S12DT512MPV@TQFP112 [DX3026]
MC9S12E128CFU@TQFP80 [DX3018]
MC9S12E128CPV@TQFP112 [DX3026]
MC9S12E128MFU@TQFP80 [DX3018]
MC9S12E128MPV@TQFP112 [DX3026]
MC9S12E128VFU@TQFP80 [DX3018]
MC9S12E128VPV@TQFP112 [DX3026]
MC9S12E256CFU@TQFP80 [DX3018]
MC9S12E256CPV@TQFP112 [DX3026]
MC9S12E256MFU@TQFP80 [DX3018]
MC9S12E256MPV@TQFP112 [DX3026]
MC9S12E256VFU@TQFP80 [DX3018]
MC9S12E256VPV@TQFP112 [DX3026]
MC9S12E32CFC@TQFP64 [DX4023]
MC9S12E32CFU@TQFP80 [DX3018]
MC9S12E32MFC@TQFP64 [DX4023]
MC9S12E32MFU@TQFP80 [DX3018]
MC9S12E32VFC@TQFP64 [DX4023]
MC9S12E32VFU@TQFP80 [DX3018]
MC9S12E64CFU@TQFP80 [DX3018]
MC9S12E64CPV@TQFP112 [DX3026]
MC9S12E64MFU@TQFP80 [DX3018]
MC9S12E64MPV@TQFP112 [DX3026]
MC9S12E64VFU@TQFP80 [DX3018]
MC9S12E64VPV@TQFP112 [DX3026]
MC9S12GC128CFA@TQFP48 [DX3007]
MC9S12GC128CPB@TQFP52 [DX3010]
MC9S12GC128MFU@TQFP80 [DX3018]
MC9S12GC128VFA@TQFP48 [DX3007]
MC9S12DT128BCFU@TQFP80 [DX3018]
MC9S12DT128BMFU@TQFP80 [DX3018]
MC9S12DT128BVFU@TQFP80 [DX3018]
MC9S12DT128CFU@TQFP80 [DX3018]
MC9S12DT128ECFU@TQFP80 [DX3018]
MC9S12DT128EMFU@TQFP80 [DX3018]
MC9S12DT128EVFU@TQFP80 [DX3018]
MC9S12DT128MFU@TQFP80 [DX3018]
MC9S12DT128VFU@TQFP80 [DX3018]
MC9S12DT256BCFU@TQFP80 [DX3018]
MC9S12DT256BMFU@TQFP80 [DX3018]
MC9S12DT256BVFU@TQFP80 [DX3018]
MC9S12DT256CCFU@TQFP80 [DX3018]
MC9S12DT256CFU@TQFP80 [DX3018]
MC9S12DT256CMPV@TQFP112 [DX3026]
MC9S12DT256CVFU@TQFP80 [DX3018]
MC9S12DT256MFU@TQFP80 [DX3018]
MC9S12DT256VFU@TQFP80 [DX3018]
MC9S12DT512CPV@TQFP112 [DX3026]
MC9S12DT512VPV@TQFP112 [DX3026]
MC9S12E128CFUE@TQFP80 [DX3018]
MC9S12E128CPVE@TQFP112 [DX3026]
MC9S12E128MFUE@TQFP80 [DX3018]
MC9S12E128MPVE@TQFP112 [DX3026]
MC9S12E128VFUE@TQFP80 [DX3018]
MC9S12E128VPVE@TQFP112 [DX3026]
MC9S12E256CFUE@TQFP80 [DX3018]
MC9S12E256CPVE@TQFP112 [DX3026]
MC9S12E256MFUE@TQFP80 [DX3018]
MC9S12E256MPVE@TQFP112 [DX3026]
MC9S12E256VFUE@TQFP80 [DX3018]
MC9S12E256VPVE@TQFP112 [DX3026]
MC9S12E32CFCE@TQFP64 [DX4023]
MC9S12E32CFUE@TQFP80 [DX3018]
MC9S12E32MFCE@TQFP64 [DX4023]
MC9S12E32MFUE@TQFP80 [DX3018]
MC9S12E32VFCE@TQFP64 [DX4023]
MC9S12E32VFUE@TQFP80 [DX3018]
MC9S12E64CFUE@TQFP80 [DX3018]
MC9S12E64CPVE@TQFP112 [DX3026]
MC9S12E64MFUE@TQFP80 [DX3018]
MC9S12E64MPVE@TQFP112 [DX3026]
MC9S12E64VFUE@TQFP80 [DX3018]
MC9S12E64VPVE@TQFP112 [DX3026]
MC9S12GC128CFU@TQFP80 [DX3018]
MC9S12GC128MFA@TQFP48 [DX3007]
MC9S12GC128MPB@TQFP52 [DX3010]
MC9S12GC128VFU@TQFP80 [DX3018]

MC9S12GC128VPB@TQFP52 [DX3010]
MC9S12GC16CFA@TQFP48 [DX3007]
MC9S12GC16CFU@TQFP80 [DX3018]
MC9S12GC16CPB@TQFP52 [DX3010]
MC9S12GC16MFA@TQFP48 [DX3007]
MC9S12GC16MFU@TQFP80 [DX3018]
MC9S12GC16MPB@TQFP52 [DX3010]
MC9S12GC16VFA@TQFP48 [DX3007]
MC9S12GC16VFU@TQFP80 [DX3018]
MC9S12GC16VPB@TQFP52 [DX3010]
MC9S12GC32CFA@TQFP48 [DX3007]
MC9S12GC32CFU@TQFP80 [DX3018]
MC9S12GC32CPB@TQFP52 [DX3010]
MC9S12GC32MFA@TQFP48 [DX3007]
MC9S12GC32MFU@TQFP80 [DX3018]
MC9S12GC32MPB@TQFP52 [DX3010]
MC9S12GC32VFA@TQFP48 [DX3007]
MC9S12GC32VFU@TQFP80 [DX3018]
MC9S12GC32VPB@TQFP52 [DX3010]
MC9S12GC64CFA@TQFP48 [DX3007]
MC9S12GC64CFU@TQFP80 [DX3018]
MC9S12GC64CPB@TQFP52 [DX3010]
MC9S12GC64MFA@TQFP48 [DX3007]
MC9S12GC64MFU@TQFP80 [DX3018]
MC9S12GC64MPB@TQFP52 [DX3010]
MC9S12GC64VFA@TQFP48 [DX3007]
MC9S12GC64VFU@TQFP80 [DX3018]
MC9S12GC64VPB@TQFP52 [DX3010]
MC9S12GC96CFA@TQFP48 [DX3007]
MC9S12GC96CFU@TQFP80 [DX3018]
MC9S12GC96CPB@TQFP52 [DX3010]
MC9S12GC96MFA@TQFP48 [DX3007]
MC9S12GC96MFU@TQFP80 [DX3018]
MC9S12GC96MPB@TQFP52 [DX3010]
MC9S12GC96VFA@TQFP48 [DX3007]
MC9S12GC96VFU@TQFP80 [DX3018]
MC9S12GC96VPB@TQFP52 [DX3010]
MC9S12H128CFV@QFP144 [DX3035]
MC9S12H128CFVE@QFP144 [DX3035]
MC9S12H128CPV@QFP112 [DX3026]
MC9S12H128CPVE@QFP112 [DX3026]
MC9S12H128MFV@QFP144 [DX3035]
MC9S12H128MFVE@QFP144 [DX3035]
MC9S12H128MPV@QFP112 [DX3026]
MC9S12H128MPVE@QFP112 [DX3026]
MC9S12H128VFV@QFP144 [DX3035]
MC9S12H128VFVE@QFP144 [DX3035]
MC9S12H128VPV@QFP112 [DX3026]
MC9S12H128VPVE@QFP112 [DX3026]
MC9S12H256CFV@QFP144 [DX3035]
MC9S12H256CFVE@QFP144 [DX3035]
MC9S12H256CPV@QFP112 [DX3026]
MC9S12H256CPVE@QFP112 [DX3026]
MC9S12H256MFV@QFP144 [DX3035]
MC9S12H256MFVE@QFP144 [DX3035]
MC9S12H256MPV@QFP112 [DX3026]
MC9S12H256MPVE@QFP112 [DX3026]
MC9S12H256VFV@QFP144 [DX3035]
MC9S12H256VFVE@QFP144 [DX3035]
MC9S12H256VPV@QFP112 [DX3026]
MC9S12H256VPVE@QFP112 [DX3026]
MC9S12HA32CLH@QFP64 [DX3011]
MC9S12HA32CLHE@QFP64 [DX3011]
MC9S12HA32CLL@QFP100 [DX3043]
MC9S12HA32CLLE@QFP100 [DX3043]
MC9S12HA32MLH@QFP64 [DX3011]
MC9S12HA32MLHE@QFP64 [DX3011]
MC9S12HA32MLL@QFP100 [DX3043]
MC9S12HA32MLLE@QFP100 [DX3043]
MC9S12HA32VLH@QFP64 [DX3011]
MC9S12HA32VLHE@QFP64 [DX3011]
MC9S12HA32VLL@QFP100 [DX3043]
MC9S12HA32VLLE@QFP100 [DX3043]
MC9S12HA48CLH@QFP64 [DX3011]
MC9S12HA48CLHE@QFP64 [DX3011]
MC9S12HA48CLL@QFP100 [DX3043]
MC9S12HA48CLLE@QFP100 [DX3043]
MC9S12HA48MLH@QFP64 [DX3011]
MC9S12HA48MLHE@QFP64 [DX3011]
MC9S12HA48MLL@QFP100 [DX3043]
MC9S12HA48MLLE@QFP100 [DX3043]
MC9S12HA48VLH@QFP64 [DX3011]
MC9S12HA48VLHE@QFP64 [DX3011]
MC9S12HA48VLL@QFP100 [DX3043]
MC9S12HA48VLLE@QFP100 [DX3043]
MC9S12HA64CLH@QFP64 [DX3011]
MC9S12HA64CLHE@QFP64 [DX3011]
MC9S12HA64CLL@QFP100 [DX3043]
MC9S12HA64CLLE@QFP100 [DX3043]
MC9S12HA64MLH@QFP64 [DX3011]
MC9S12HA64MLHE@QFP64 [DX3011]
MC9S12HA64MLL@QFP100 [DX3043]
MC9S12HA64MLLE@QFP100 [DX3043]
MC9S12HA64VLH@QFP64 [DX3011]
MC9S12HA64VLHE@QFP64 [DX3011]
MC9S12HA64VLL@QFP100 [DX3043]

MC9S12HA64VLLE@QFP100 [DX3043]
MC9S12HN64CAL@LQFP112 [DX3026]
MC9S12HN64CPV@LQFP112 [DX3026]
MC9S12HN64MAL@LQFP112 [DX3026]
MC9S12HN64MPV@LQFP112 [DX3026]
MC9S12HN64VAL@LQFP112 [DX3026]
MC9S12HN64VPV@LQFP112 [DX3026]
MC9S12HY32CLHE@QFP64 [DX3011]
MC9S12HY32CLLE@QFP100 [DX3043]
MC9S12HY32MLHE@QFP64 [DX3011]
MC9S12HY32MLLE@QFP100 [DX3043]
MC9S12HY32VLHE@QFP64 [DX3011]
MC9S12HY32VLLE@QFP100 [DX3043]
MC9S12HY48CLHE@QFP64 [DX3011]
MC9S12HY48CLLE@QFP100 [DX3043]
MC9S12HY48MLHE@QFP64 [DX3011]
MC9S12HY48MLLE@QFP100 [DX3043]
MC9S12HY48VLHE@QFP64 [DX3011]
MC9S12HY48VLLE@QFP100 [DX3043]
MC9S12HY64CLHE@QFP64 [DX3011]
MC9S12HY64CLLE@QFP100 [DX3043]
MC9S12HY64MLHE@QFP64 [DX3011]
MC9S12HY64MLLE@QFP100 [DX3043]
MC9S12HY64VLHE@QFP64 [DX3011]
MC9S12HY64VLLE@QFP100 [DX3043]
MC9S12HZ128CAL@LQFP112 [DX3026]
MC9S12HZ128CPV@LQFP112 [DX3026]
MC9S12HZ128MAL@LQFP112 [DX3026]
MC9S12HZ128MPV@LQFP112 [DX3026]
MC9S12HZ128VAL@LQFP112 [DX3026]
MC9S12HZ128VPV@LQFP112 [DX3026]
MC9S12HZ256CAL@LQFP112 [DX3026]
MC9S12HZ256CPV@LQFP112 [DX3026]
MC9S12HZ256MAL@LQFP112 [DX3026]
MC9S12HZ256MPV@LQFP112 [DX3026]
MC9S12HZ256VAL@LQFP112 [DX3026]
MC9S12HZ256VPV@LQFP112 [DX3026]
MC9S12HZ64CAL@LQFP112 [DX3026]
MC9S12HZ64CPV@LQFP112 [DX3026]
MC9S12HZ64MAL@LQFP112 [DX3026]
MC9S12HZ64MPV@LQFP112 [DX3026]
MC9S12HZ64VAL@LQFP112 [DX3026]
MC9S12HZ64VPV@LQFP112 [DX3026]
MC9S12KG256CPV@LQFP112 [DX3026]
MC9S12KG256MPV@LQFP112 [DX3026]
MC9S12KG256VPV@LQFP112 [DX3026]
MC9S12KT256MPV@LQFP112 [DX3026]
MC9S12NE64CPV@LQFP112 [DX3026]
MC9S12HN64CAA@TQFP80 [DX3018]
MC9S12HN64CFU@TQFP80 [DX3018]
MC9S12HN64MAA@TQFP80 [DX3018]
MC9S12HN64MFU@TQFP80 [DX3018]
MC9S12HN64VAA@TQFP80 [DX3018]
MC9S12HN64VFU@TQFP80 [DX3018]
MC9S12HY32CLH@QFP64 [DX3011]
MC9S12HY32CLL@QFP100 [DX3043]
MC9S12HY32MLH@QFP64 [DX3011]
MC9S12HY32MLL@QFP100 [DX3043]
MC9S12HY32VLH@QFP64 [DX3011]
MC9S12HY32VLL@QFP100 [DX3043]
MC9S12HY48CLH@QFP64 [DX3011]
MC9S12HY48CLL@QFP100 [DX3043]
MC9S12HY48MLH@QFP64 [DX3011]
MC9S12HY48MLL@QFP100 [DX3043]
MC9S12HY48VLH@QFP64 [DX3011]
MC9S12HY48VLL@QFP100 [DX3043]
MC9S12HY64CLH@QFP64 [DX3011]
MC9S12HY64CLL@QFP100 [DX3043]
MC9S12HY64MLH@QFP64 [DX3011]
MC9S12HY64MLL@QFP100 [DX3043]
MC9S12HY64VLH@QFP64 [DX3011]
MC9S12HY64VLL@QFP100 [DX3043]
MC9S12HZ128CAA@TQFP80 [DX3018]
MC9S12HZ128CFU@TQFP80 [DX3018]
MC9S12HZ128MAA@TQFP80 [DX3018]
MC9S12HZ128MFU@TQFP80 [DX3018]
MC9S12HZ128VAA@TQFP80 [DX3018]
MC9S12HZ128VFU@TQFP80 [DX3018]
MC9S12HZ256CAA@TQFP80 [DX3018]
MC9S12HZ256CFU@TQFP80 [DX3018]
MC9S12HZ256MAA@TQFP80 [DX3018]
MC9S12HZ256MFU@TQFP80 [DX3018]
MC9S12HZ256VAA@TQFP80 [DX3018]
MC9S12HZ256VFU@TQFP80 [DX3018]
MC9S12HZ64CAA@TQFP80 [DX3018]
MC9S12HZ64CFU@TQFP80 [DX3018]
MC9S12HZ64MAA@TQFP80 [DX3018]
MC9S12HZ64MFU@TQFP80 [DX3018]
MC9S12HZ64VAA@TQFP80 [DX3018]
MC9S12HZ64VFU@TQFP80 [DX3018]
MC9S12KG256CFU@TQFP80 [DX3018]
MC9S12KG256MFU@TQFP80 [DX3018]
MC9S12KG256VFU@TQFP80 [DX3018]
MC9S12KT256CPV@LQFP112 [DX3026]
MC9S12KT256VPV@LQFP112 [DX3026]
MC9S12NE64CPVE@LQFP112 [DX3026]

MC9S12NE64VTU@TQFP80 [DX3017]
MC9S12NE64VTUE@TQFP80 [DX3017]
MC9S12P128CFT@QFN48 [DX4021]
MC9S12P128CLH@QFP64 [DX3011]
MC9S12P128CQK@QFP80 [DX3018]
MC9S12P128MFT@QFN48 [DX4021]
MC9S12P128MLH@QFP64 [DX3011]
MC9S12P128MQK@QFP80 [DX3018]
MC9S12P128VFT@QFN48 [DX4021]
MC9S12P128VLH@QFP64 [DX3011]
MC9S12P128VQK@QFP80 [DX3018]
MC9S12P32CFT@QFN48 [DX4021]
MC9S12P32CLH@QFP64 [DX3011]
MC9S12P32CQK@QFP80 [DX3018]
MC9S12P32MFT@QFN48 [DX4021]
MC9S12P32MLH@QFP64 [DX3011]
MC9S12P32MQK@QFP80 [DX3018]
MC9S12P32VFT@QFN48 [DX4021]
MC9S12P32VLH@QFP64 [DX3011]
MC9S12P32VQK@QFP80 [DX3018]
MC9S12P64CFT@QFN48 [DX4021]
MC9S12P64CLH@QFP64 [DX3011]
MC9S12P64CQK@QFP80 [DX3018]
MC9S12P64MFT@QFN48 [DX4021]
MC9S12P64MLH@QFP64 [DX3011]
MC9S12P64MQK@QFP80 [DX3018]
MC9S12P64VFT@QFN48 [DX4021]
MC9S12P64VLH@QFP64 [DX3011]
MC9S12P64VQK@QFP80 [DX3018]
MC9S12P96CFT@QFN48 [DX4021]
MC9S12P96CLH@QFP64 [DX3011]
MC9S12P96CQK@QFP80 [DX3018]
MC9S12P96MFT@QFN48 [DX4021]
MC9S12P96MLH@QFP64 [DX3011]
MC9S12P96MQK@QFP80 [DX3018]
MC9S12P96VFT@QFN48 [DX4021]
MC9S12P96VLH@QFP64 [DX3011]
MC9S12P96VQK@QFP80 [DX3018]
MC9S12Q128CFA@TQFP48 [DX3007]
MC9S12Q128CFAE@TQFP48 [DX3007]
MC9S12Q128CFU@TQFP80 [DX3018]
MC9S12Q128CFUE@TQFP80 [DX3018]
MC9S12Q128CPB@TQFP52 [DX3010]
MC9S12Q128CPBE@TQFP52 [DX3010]
MC9S12Q128MFA@TQFP48 [DX3007]
MC9S12Q128MFAE@TQFP48 [DX3007]
MC9S12Q128MFU@TQFP80 [DX3018]
MC9S12Q128MFUE@TQFP80 [DX3018]
MC9S12Q128MPB@TQFP52 [DX3010]
MC9S12Q128MPBE@TQFP52 [DX3010]
MC9S12Q128VFA@TQFP48 [DX3007]
MC9S12Q128VFAE@TQFP48 [DX3007]
MC9S12Q128VFU@TQFP80 [DX3018]
MC9S12Q128VFUE@TQFP80 [DX3018]
MC9S12Q128VPB@TQFP52 [DX3010]
MC9S12Q128VPBE@TQFP52 [DX3010]
MC9S12Q32CFA@TQFP48 [DX3007]
MC9S12Q32CFAE@TQFP48 [DX3007]
MC9S12Q32CFU@TQFP80 [DX3018]
MC9S12Q32CFUE@TQFP80 [DX3018]
MC9S12Q32CPB@TQFP52 [DX3010]
MC9S12Q32CPBE@TQFP52 [DX3010]
MC9S12Q32MFA@TQFP48 [DX3007]
MC9S12Q32MFAE@TQFP48 [DX3007]
MC9S12Q32MFU@TQFP80 [DX3018]
MC9S12Q32MFUE@TQFP80 [DX3018]
MC9S12Q32MPB@TQFP52 [DX3010]
MC9S12Q32MPBE@TQFP52 [DX3010]
MC9S12Q32VFA@TQFP48 [DX3007]
MC9S12Q32VFAE@TQFP48 [DX3007]
MC9S12Q32VFU@TQFP80 [DX3018]
MC9S12Q32VFUE@TQFP80 [DX3018]
MC9S12Q32VPB@TQFP52 [DX3010]
MC9S12Q32VPBE@TQFP52 [DX3010]
MC9S12Q64CFA@TQFP48 [DX3007]
MC9S12Q64CFAE@TQFP48 [DX3007]
MC9S12Q64CFU@TQFP80 [DX3018]
MC9S12Q64CFUE@TQFP80 [DX3018]
MC9S12Q64CPB@TQFP52 [DX3010]
MC9S12Q64CPBE@TQFP52 [DX3010]
MC9S12Q64MFA@TQFP48 [DX3007]
MC9S12Q64MFAE@TQFP48 [DX3007]
MC9S12Q64MFU@TQFP80 [DX3018]
MC9S12Q64MFUE@TQFP80 [DX3018]
MC9S12Q64MPB@TQFP52 [DX3010]
MC9S12Q64MPBE@TQFP52 [DX3010]
MC9S12Q64VFA@TQFP48 [DX3007]
MC9S12Q64VFAE@TQFP48 [DX3007]
MC9S12Q64VFU@TQFP80 [DX3018]
MC9S12Q64VFUE@TQFP80 [DX3018]
MC9S12Q64VPB@TQFP52 [DX3010]
MC9S12Q64VPBE@TQFP52 [DX3010]
MC9S12Q96CFA@TQFP48 [DX3007]
MC9S12Q96CFAE@TQFP48 [DX3007]
MC9S12Q96CFU@TQFP80 [DX3018]
MC9S12Q96CFUE@TQFP80 [DX3018]

MC9S12Q96CPB@TQFP52 [DX3010]
MC9S12Q96CPBE@TQFP52 [DX3010]
MC9S12Q96MFA@TQFP48 [DX3007]
MC9S12Q96MFAE@TQFP48 [DX3007]
MC9S12Q96MFU@TQFP80 [DX3018]
MC9S12Q96MFUE@TQFP80 [DX3018]
MC9S12Q96MPB@TQFP52 [DX3010]
MC9S12Q96MPBE@TQFP52 [DX3010]
MC9S12Q96VFA@TQFP48 [DX3007]
MC9S12Q96VFAE@TQFP48 [DX3007]
MC9S12Q96VFU@TQFP80 [DX3018]
MC9S12Q96VFUE@TQFP80 [DX3018]
MC9S12Q96VPB@TQFP52 [DX3010]
MC9S12Q96VPBE@TQFP52 [DX3010]
MC9S12T64CPK16@TQFP80 [DX3016]
MC9S12T64MPK16@TQFP80 [DX3016]
MC9S12T64VPK16@TQFP80 [DX3016]
MC9S12UF32PB@QFP64 [DX3011]
MC9S12UF32PBE@QFP64 [DX3011]
MC9S12UF32PU@QFP100 [DX3021]
MC9S12UF32PUE@QFP100 [DX3021]
MC9S12XA128CAA@TQFP80 [DX3018]
MC9S12XA128CAL@TQFP112 [DX3026]
MC9S12XA128CFU@TQFP80 [DX3018]
MC9S12XA128CPV@TQFP112 [DX3026]
MC9S12XA128MAA@TQFP80 [DX3018]
MC9S12XA128MAL@TQFP112 [DX3026]
MC9S12XA128MFU@TQFP80 [DX3018]
MC9S12XA128MPV@TQFP112 [DX3026]
MC9S12XA128VAA@TQFP80 [DX3018]
MC9S12XA128VAL@TQFP112 [DX3026]
MC9S12XA128VFU@TQFP80 [DX3018]
MC9S12XA128VPV@TQFP112 [DX3026]
MC9S12XA256CAA@TQFP80 [DX3018]
MC9S12XA256CAG@LQFP144 [DX3035]
MC9S12XA256CAL@TQFP112 [DX3026]
MC9S12XA256CFU@TQFP80 [DX3018]
MC9S12XA256CFV@LQFP144 [DX3035]
MC9S12XA256CPV@TQFP112 [DX3026]
MC9S12XA256MAA@TQFP80 [DX3018]
MC9S12XA256MAG@LQFP144 [DX3035]
MC9S12XA256MAL@TQFP112 [DX3026]
MC9S12XA256MFU@TQFP80 [DX3018]
MC9S12XA256MFV@LQFP144 [DX3035]
MC9S12XA256MPV@TQFP112 [DX3026]
MC9S12XA256VAA@TQFP80 [DX3018]
MC9S12XA256VAG@LQFP144 [DX3035]
MC9S12XA256VAL@TQFP112 [DX3026]
MC9S12XA256VFU@TQFP80 [DX3018]
MC9S12XA256VFV@LQFP144 [DX3035]
MC9S12XA256VPV@TQFP112 [DX3026]
MC9S12XA512CAA@TQFP80 [DX3018]
MC9S12XA512CAG@LQFP144 [DX3035]
MC9S12XA512CAL@TQFP112 [DX3026]
MC9S12XA512CFU@TQFP80 [DX3018]
MC9S12XA512CFV@LQFP144 [DX3035]
MC9S12XA512CPV@TQFP112 [DX3026]
MC9S12XA512MAA@TQFP80 [DX3018]
MC9S12XA512MAG@LQFP144 [DX3035]
MC9S12XA512MAL@TQFP112 [DX3026]
MC9S12XA512MFU@TQFP80 [DX3018]
MC9S12XA512MFV@LQFP144 [DX3035]
MC9S12XA512MPV@TQFP112 [DX3026]
MC9S12XA512VAA@TQFP80 [DX3018]
MC9S12XA512VAG@LQFP144 [DX3035]
MC9S12XA512VAL@TQFP112 [DX3026]
MC9S12XA512VFU@TQFP80 [DX3018]
MC9S12XA512VFV@LQFP144 [DX3035]
MC9S12XA512VPV@TQFP112 [DX3026]
MC9S12XB128CAA@TQFP80 [DX3018]
MC9S12XB128CAL@TQFP112 [DX3026]
MC9S12XB128CFU@TQFP80 [DX3018]
MC9S12XB128CPV@TQFP112 [DX3026]
MC9S12XB128MAA@TQFP80 [DX3018]
MC9S12XB128MAL@TQFP112 [DX3026]
MC9S12XB128MFU@TQFP80 [DX3018]
MC9S12XB128MPV@TQFP112 [DX3026]
MC9S12XB128VAA@TQFP80 [DX3018]
MC9S12XB128VAL@TQFP112 [DX3026]
MC9S12XB128VFU@TQFP80 [DX3018]
MC9S12XB128VPV@TQFP112 [DX3026]
MC9S12XB256CAA@TQFP80 [DX3018]
MC9S12XB256CAL@TQFP112 [DX3026]
MC9S12XB256CFU@TQFP80 [DX3018]
MC9S12XB256CPV@TQFP112 [DX3026]
MC9S12XB256MAA@TQFP80 [DX3018]
MC9S12XB256MAL@TQFP112 [DX3026]
MC9S12XB256MFU@TQFP80 [DX3018]
MC9S12XB256MPV@TQFP112 [DX3026]
MC9S12XB256VAA@TQFP80 [DX3018]
MC9S12XB256VAL@TQFP112 [DX3026]
MC9S12XB256VFU@TQFP80 [DX3018]
MC9S12XB256VPV@TQFP112 [DX3026]
MC9S12XD128CAA@TQFP80 [DX3018]
MC9S12XD128CAL@TQFP112 [DX3026]
MC9S12XD128CFU@TQFP80 [DX3018]

MC9S12XD128CPV@TQFP112 [DX3026]
MC9S12XD128MAA@TQFP80 [DX3018]
MC9S12XD128MAL@TQFP112 [DX3026]
MC9S12XD128MFU@TQFP80 [DX3018]
MC9S12XD128MPV@TQFP112 [DX3026]
MC9S12XD128VAA@TQFP80 [DX3018]
MC9S12XD128VAL@TQFP112 [DX3026]
MC9S12XD128VFU@TQFP80 [DX3018]
MC9S12XD128VPV@TQFP112 [DX3026]
MC9S12XD256CAA@TQFP80 [DX3018]
MC9S12XD256CAG@LQFP144 [DX3035]
MC9S12XD256CAL@TQFP112 [DX3026]
MC9S12XD256CFU@TQFP80 [DX3018]
MC9S12XD256CFV@LQFP144 [DX3035]
MC9S12XD256CPV@TQFP112 [DX3026]
MC9S12XD256MAA@TQFP80 [DX3018]
MC9S12XD256MAG@LQFP144 [DX3035]
MC9S12XD256MAL@TQFP112 [DX3026]
MC9S12XD256MFU@TQFP80 [DX3018]
MC9S12XD256MFV@LQFP144 [DX3035]
MC9S12XD256MPV@TQFP112 [DX3026]
MC9S12XD256VAA@TQFP80 [DX3018]
MC9S12XD256VAG@LQFP144 [DX3035]
MC9S12XD256VAL@TQFP112 [DX3026]
MC9S12XD256VFU@TQFP80 [DX3018]
MC9S12XD256VFV@LQFP144 [DX3035]
MC9S12XD256VPV@TQFP112 [DX3026]
MC9S12XD64CAA@TQFP80 [DX3018]
MC9S12XD64CFU@TQFP80 [DX3018]
MC9S12XD64MAA@TQFP80 [DX3018]
MC9S12XD64MFU@TQFP80 [DX3018]
MC9S12XD64VAA@TQFP80 [DX3018]
MC9S12XD64VFU@TQFP80 [DX3018]
MC9S12XDG128CAA@TQFP80 [DX3018]
MC9S12XDG128CAL@TQFP112 [DX3026]
MC9S12XDG128CFU@TQFP80 [DX3018]
MC9S12XDG128CPV@TQFP112 [DX3026]
MC9S12XDG128MAA@TQFP80 [DX3018]
MC9S12XDG128MAL@TQFP112 [DX3026]
MC9S12XDG128MFU@TQFP80 [DX3018]
MC9S12XDG128MPV@TQFP112 [DX3026]
MC9S12XDG128VAA@TQFP80 [DX3018]
MC9S12XDG128VAL@TQFP112 [DX3026]
MC9S12XDG128VFU@TQFP80 [DX3018]
MC9S12XDG128VPV@TQFP112 [DX3026]
MC9S12XDP512CAA@TQFP80 [DX3018]
MC9S12XDP512CAG@LQFP144 [DX3035]
MC9S12XDP512CAL@TQFP112 [DX3026]
MC9S12XDP512CFU@TQFP80 [DX3018]
MC9S12XDP512CFV@LQFP144 [DX3035]
MC9S12XDP512CPV@TQFP112 [DX3026]
MC9S12XDP512MAA@TQFP80 [DX3018]
MC9S12XDP512MAG@LQFP144 [DX3035]
MC9S12XDP512MAL@TQFP112 [DX3026]
MC9S12XDP512MFU@TQFP80 [DX3018]
MC9S12XDP512MFV@LQFP144 [DX3035]
MC9S12XDP512MPV@TQFP112 [DX3026]
MC9S12XDP512VAA@TQFP80 [DX3018]
MC9S12XDP512VAG@LQFP144 [DX3035]
MC9S12XDP512VAL@TQFP112 [DX3026]
MC9S12XDP512VFV@LQFP144 [DX3035]
MC9S12XDP512VPU@TQFP80 [DX3018]
MC9S12XDP512VPV@TQFP112 [DX3026]
MC9S12XDQ256CAA@TQFP80 [DX3018]
MC9S12XDQ256CAG@LQFP144 [DX3035]
MC9S12XDQ256CAL@TQFP112 [DX3026]
MC9S12XDQ256CFU@TQFP80 [DX3018]
MC9S12XDQ256CFV@LQFP144 [DX3035]
MC9S12XDQ256CPV@TQFP112 [DX3026]
MC9S12XDQ256MAA@TQFP80 [DX3018]
MC9S12XDQ256MAG@LQFP144 [DX3035]
MC9S12XDQ256MAL@TQFP112 [DX3026]
MC9S12XDQ256MFU@TQFP80 [DX3018]
MC9S12XDQ256MFV@LQFP144 [DX3035]
MC9S12XDQ256MPV@TQFP112 [DX3026]
MC9S12XDQ256VAA@TQFP80 [DX3018]
MC9S12XDQ256VAG@LQFP144 [DX3035]
MC9S12XDQ256VAL@TQFP112 [DX3026]
MC9S12XDQ256VFU@TQFP80 [DX3018]
MC9S12XDQ256VFV@LQFP144 [DX3035]
MC9S12XDQ256VPV@TQFP112 [DX3026]
MC9S12XDT256CAA@TQFP80 [DX3018]
MC9S12XDT256CAG@LQFP144 [DX3035]
MC9S12XDT256CAL@TQFP112 [DX3026]
MC9S12XDT256CFU@TQFP80 [DX3018]
MC9S12XDT256CFV@LQFP144 [DX3035]
MC9S12XDT256CPV@TQFP112 [DX3026]
MC9S12XDT256MAA@TQFP80 [DX3018]
MC9S12XDT256MAG@LQFP144 [DX3035]
MC9S12XDT256MAL@TQFP112 [DX3026]
MC9S12XDT256MFU@TQFP80 [DX3018]
MC9S12XDT256MFV@LQFP144 [DX3035]
MC9S12XDT256MPV@TQFP112 [DX3026]
MC9S12XDT256VAA@TQFP80 [DX3018]
MC9S12XDT256VAG@LQFP144 [DX3035]
MC9S12XDT256VAL@TQFP112 [DX3026]

MC9S12XDT256VFU@TQFP80 [DX3018]
MC9S12XDT256VFV@LQFP144 [DX3035]
MC9S12XDT256VPV@TQFP112 [DX3026]
MC9S12XDT384CAA@TQFP80 [DX3018]
MC9S12XDT384CAG@LQFP144 [DX3035]
MC9S12XDT384CAL@TQFP112 [DX3026]
MC9S12XDT384CFV@LQFP144 [DX3035]
MC9S12XDT384CPU@TQFP80 [DX3018]
MC9S12XDT384CPV@TQFP112 [DX3026]
MC9S12XDT384MAA@TQFP80 [DX3018]
MC9S12XDT384MAG@LQFP144 [DX3035]
MC9S12XDT384MAL@TQFP112 [DX3026]
MC9S12XDT384MFV@LQFP144 [DX3035]
MC9S12XDT384MPU@TQFP80 [DX3018]
MC9S12XDT384MPV@TQFP112 [DX3026]
MC9S12XDT384VAA@TQFP80 [DX3018]
MC9S12XDT384VAG@LQFP144 [DX3035]
MC9S12XDT384VAL@TQFP112 [DX3026]
MC9S12XDT384VFV@LQFP144 [DX3035]
MC9S12XDT384VPU@TQFP80 [DX3018]
MC9S12XDT384VPV@TQFP112 [DX3026]
MC9S12XDT512CAA@TQFP80 [DX3018]
MC9S12XDT512CAG@LQFP144 [DX3035]
MC9S12XDT512CAL@TQFP112 [DX3026]
MC9S12XDT512CFU@TQFP80 [DX3018]
MC9S12XDT512CFV@LQFP144 [DX3035]
MC9S12XDT512CPV@TQFP112 [DX3026]
MC9S12XDT512MAA@TQFP80 [DX3018]
MC9S12XDT512MAG@LQFP144 [DX3035]
MC9S12XDT512MAL@TQFP112 [DX3026]
MC9S12XDT512MFU@TQFP80 [DX3018]
MC9S12XDT512MFV@LQFP144 [DX3035]
MC9S12XDT512MPV@TQFP112 [DX3026]
MC9S12XDT512VAA@TQFP80 [DX3018]
MC9S12XDT512VAG@LQFP144 [DX3035]
MC9S12XDT512VAL@TQFP112 [DX3026]
MC9S12XDT512VFU@TQFP80 [DX3018]
MC9S12XDT512VFV@LQFP144 [DX3035]
MC9S12XDT512VPV@TQFP112 [DX3026]
MC9S12XEA128CAA@TQFP80 [DX3018]
MC9S12XEA128CAL@TQFP112 [DX3026]
MC9S12XEA128MAA@TQFP80 [DX3018]
MC9S12XEA128MAL@TQFP112 [DX3026]
MC9S12XEA128VAA@TQFP80 [DX3018]
MC9S12XEA128VAL@TQFP112 [DX3026]
MC9S12XEA256CAA@TQFP80 [DX3018]
MC9S12XEA256CAG@LQFP144 [DX3035]
MC9S12XEA256CAL@TQFP112 [DX3026]
MC9S12XEA256MAA@TQFP80 [DX3018]
MC9S12XEA256MAG@LQFP144 [DX3035]
MC9S12XEA256MAL@TQFP112 [DX3026]
MC9S12XEA256VAA@TQFP80 [DX3018]
MC9S12XEA256VAG@LQFP144 [DX3035]
MC9S12XEA256VAL@TQFP112 [DX3026]
MC9S12XEG128CAA@TQFP80 [DX3018]
MC9S12XEG128CAL@TQFP112 [DX3026]
MC9S12XEG128MAA@TQFP80 [DX3018]
MC9S12XEG128MAL@TQFP112 [DX3026]
MC9S12XEG128VAA@TQFP80 [DX3018]
MC9S12XEG128VAL@TQFP112 [DX3026]
MC9S12XEG256CAA@QFP80 [DX3018]
MC9S12XEG256CAL@TQFP112 [DX3026]
MC9S12XEG256MAA@QFP80 [DX3018]
MC9S12XEG256MAL@TQFP112 [DX3026]
MC9S12XEG256VAA@QFP80 [DX3018]
MC9S12XEG256VAL@TQFP112 [DX3026]
MC9S12XEG384CAA@TQFP80 [DX3018]
MC9S12XEG384CAG@LQFP144 [DX3035]
MC9S12XEG384CAL@TQFP112 [DX3026]
MC9S12XEG384MAA@TQFP80 [DX3018]
MC9S12XEG384MAG@LQFP144 [DX3035]
MC9S12XEG384MAL@TQFP112 [DX3026]
MC9S12XEG384VAA@TQFP80 [DX3018]
MC9S12XEG384VAG@LQFP144 [DX3035]
MC9S12XEG384VAL@TQFP112 [DX3026]
MC9S12XEP100CAG@LQFP144 [DX3035]
MC9S12XEP100CAL@TQFP112 [DX3026]
MC9S12XEP100MAG@LQFP144 [DX3035]
MC9S12XEP100MAL@TQFP112 [DX3026]
MC9S12XEP100VAG@LQFP144 [DX3035]
MC9S12XEP100VAL@TQFP112 [DX3026]
MC9S12XEP768CAG@LQFP144 [DX3035]
MC9S12XEP768CAL@TQFP112 [DX3026]
MC9S12XEP768MAG@LQFP144 [DX3035]
MC9S12XEP768MAL@TQFP112 [DX3026]
MC9S12XEP768VAG@LQFP144 [DX3035]
MC9S12XEP768VAL@TQFP112 [DX3026]
MC9S12XEQ384CAA@TQFP80 [DX3018]
MC9S12XEQ384CAG@LQFP144 [DX3035]
MC9S12XEQ384CAL@TQFP112 [DX3026]
MC9S12XEQ384MAA@TQFP80 [DX3018]
MC9S12XEQ384MAG@LQFP144 [DX3035]
MC9S12XEQ384MAL@TQFP112 [DX3026]
MC9S12XEQ384VAA@TQFP80 [DX3018]
MC9S12XEQ384VAG@LQFP144 [DX3035]
MC9S12XEQ384VAL@TQFP112 [DX3026]

MC9S12XEQ512CAA@TQFP80 [DX3018]
MC9S12XEQ512CAG@LQFP144 [DX3035]
MC9S12XEQ512CAL@TQFP112 [DX3026]
MC9S12XEQ512MAA@TQFP80 [DX3018]
MC9S12XEQ512MAG@LQFP144 [DX3035]
MC9S12XEQ512MAL@TQFP112 [DX3026]
MC9S12XEQ512VAA@TQFP80 [DX3018]
MC9S12XEQ512VAG@LQFP144 [DX3035]
MC9S12XEQ512VAL@TQFP112 [DX3026]
MC9S12XET256CAA@TQFP80 [DX3018]
MC9S12XET256CAG@LQFP144 [DX3035]
MC9S12XET256CAL@TQFP112 [DX3026]
MC9S12XET256MAA@TQFP80 [DX3018]
MC9S12XET256MAG@LQFP144 [DX3035]
MC9S12XET256MAL@TQFP112 [DX3026]
MC9S12XET256VAA@TQFP80 [DX3018]
MC9S12XET256VAG@LQFP144 [DX3035]
MC9S12XET256VAL@TQFP112 [DX3026]
MC9S12XF128CAG@QFP144 [DX3035]
MC9S12XF128CAL@QFP112 [DX3026]
MC9S12XF128CLH@QFP64 [DX3011]
MC9S12XF128MAG@QFP144 [DX3035]
MC9S12XF128MAL@QFP112 [DX3026]
MC9S12XF128MLH@QFP64 [DX3011]
MC9S12XF128VAG@QFP144 [DX3035]
MC9S12XF128VAL@QFP112 [DX3026]
MC9S12XF128VLH@QFP64 [DX3011]
MC9S12XF256CAG@QFP144 [DX3035]
MC9S12XF256CAL@QFP112 [DX3026]
MC9S12XF256CLH@QFP64 [DX3011]
MC9S12XF256MAG@QFP144 [DX3035]
MC9S12XF256MAL@QFP112 [DX3026]
MC9S12XF256MLH@QFP64 [DX3011]
MC9S12XF256VAG@QFP144 [DX3035]
MC9S12XF256VAL@QFP112 [DX3026]
MC9S12XF256VLH@QFP64 [DX3011]
MC9S12XF384CAG@QFP144 [DX3035]
MC9S12XF384CAL@QFP112 [DX3026]
MC9S12XF384CLH@QFP64 [DX3011]
MC9S12XF384MAG@QFP144 [DX3035]
MC9S12XF384MAL@QFP112 [DX3026]
MC9S12XF384MLH@QFP64 [DX3011]
MC9S12XF384VAG@QFP144 [DX3035]
MC9S12XF384VAL@QFP112 [DX3026]
MC9S12XF384VLH@QFP64 [DX3011]
MC9S12XF512CAG@QFP144 [DX3035]
MC9S12XF512CAL@QFP112 [DX3026]
MC9S12XF512CLH@QFP64 [DX3011]
MC9S12XF512MAG@QFP144 [DX3035]
MC9S12XF512MAL@QFP112 [DX3026]
MC9S12XF512MLH@QFP64 [DX3011]
MC9S12XF512VAG@QFP144 [DX3035]
MC9S12XF512VAL@QFP112 [DX3026]
MC9S12XF512VLH@QFP64 [DX3011]
MC9S12XHY128CLL [DX3021]
MC9S12XHY128CLM [DX3026]
MC9S12XHY128MLL [DX3021]
MC9S12XHY128MLM [DX3026]
MC9S12XHY128VLL [DX3021]
MC9S12XHY128VLM [DX3026]
MC9S12XHY256CLL [DX3021]
MC9S12XHY256CLM [DX3026]
MC9S12XHY256MLL [DX3021]
MC9S12XHY256MLM [DX3026]
MC9S12XHY256VLL [DX3021]
MC9S12XHY256VLM [DX3026]
MC9S12XHZ256CAG@LQFP144 [DX3035]
MC9S12XHZ256CAL@TQFP112 [DX3026]
MC9S12XHZ256MAG@LQFP144 [DX3035]
MC9S12XHZ256MAL@TQFP112 [DX3026]
MC9S12XHZ256VAG@LQFP144 [DX3035]
MC9S12XHZ256VAL@TQFP112 [DX3026]
MC9S12XHZ384CAG@LQFP144 [DX3035]
MC9S12XHZ384CAL@TQFP112 [DX3026]
MC9S12XHZ384MAG@LQFP144 [DX3035]
MC9S12XHZ384MAL@TQFP112 [DX3026]
MC9S12XHZ384VAG@LQFP144 [DX3035]
MC9S12XHZ384VAL@TQFP112 [DX3026]
MC9S12XHZ512CAG@LQFP144 [DX3035]
MC9S12XHZ512CAL@TQFP112 [DX3026]
MC9S12XHZ512MAG@LQFP144 [DX3035]
MC9S12XHZ512MAL@TQFP112 [DX3026]
MC9S12XHZ512VAG@LQFP144 [DX3035]
MC9S12XHZ512VAL@TQFP112 [DX3026]
MC9S12XS128CAA@QFP80 [DX3018]
MC9S12XS128CAE@QFP64 [DX3011]
MC9S12XS128CAL@QFP112 [DX3026]
MC9S12XS128MAA@QFP80 [DX3018]
MC9S12XS128MAE@QFP64 [DX3011]
MC9S12XS128MAL@QFP112 [DX3026]
MC9S12XS128VAA@QFP80 [DX3018]
MC9S12XS128VAE@QFP64 [DX3011]
MC9S12XS128VAL@QFP112 [DX3026]
MC9S12XS256CAA@QFP80 [DX3018]
MC9S12XS256CAE@QFP64 [DX3011]
MC9S12XS256CAL@QFP112 [DX3026]

MC9S12XS256MAA@QFP80 [DX3018]
MC9S12XS256MAE@QFP64 [DX3011]
MC9S12XS256MAL@QFP112 [DX3026]
MC9S12XS256VAA@QFP80 [DX3018]
MC9S12XS256VAE@QFP64 [DX3011]
MC9S12XS256VAL@QFP112 [DX3026]
MC9S12XS64CAA@QFP80 [DX3018]
MC9S12XS64CAE@QFP64 [DX3011]
MC9S12XS64CAL@QFP112 [DX3026]
MC9S12XS64MAA@QFP80 [DX3018]
MC9S12XS64MAE@QFP64 [DX3011]
MC9S12XS64MAL@QFP112 [DX3026]
MC9S12XS64VAA@QFP80 [DX3018]
MC9S12XS64VAE@QFP64 [DX3011]
MC9S12XS64VAL@QFP112 [DX3026]
MCF51AC128ACFUE@QFP64 [DX3014]
MCF51AC128ACLKE@LQFP80 [DX3017]
MCF51AC128ACPUE@LQFP64 [DX3011]
MCF51AC128AMFUE@QFP64 [DX3014]
MCF51AC128AMLKE@LQFP80 [DX3017]
MCF51AC128AMPUE@LQFP64 [DX3011]
MCF51AC128AVFUE@QFP64 [DX3014]
MCF51AC128AVLKE@LQFP80 [DX3017]
MCF51AC128AVPUE@LQFP64 [DX3011]
MCF51AC128BCFUE@QFP64 [DX3014]
MCF51AC128BCLKE@LQFP80 [DX3017]
MCF51AC128BCPUE@LQFP64 [DX3011]
MCF51AC128BMFUE@QFP64 [DX3014]
MCF51AC128BMLKE@LQFP80 [DX3017]
MCF51AC128BMPUE@LQFP64 [DX3011]
MCF51AC128BVFUE@QFP64 [DX3014]
MCF51AC128BVLKE@LQFP80 [DX3017]
MCF51AC128BVPUE@LQFP64 [DX3011]
MCF51AC128CCFUE@QFP64 [DX3014]
MCF51AC128CCLKE@LQFP80 [DX3017]
MCF51AC128CCPUE@LQFP64 [DX3011]
MCF51AC128CMFUE@QFP64 [DX3014]
MCF51AC128CMLKE@LQFP80 [DX3017]
MCF51AC128CMPUE@LQFP64 [DX3011]
MCF51AC128CVFUE@QFP64 [DX3014]
MCF51AC128CVLKE@LQFP80 [DX3017]
MCF51AC128CVPUE@LQFP64 [DX3011]
MCF51AC256ACFUE@QFP64 [DX3014]
MCF51AC256ACLKE@LQFP80 [DX3017]
MCF51AC256ACPUE@LQFP64 [DX3011]
MCF51AC256AMFUE@QFP64 [DX3014]
MCF51AC256AMLKE@LQFP80 [DX3017]
MCF51AC256AMPUE@LQFP64 [DX3011]
MCF51AC256AVFUE@QFP64 [DX3014]
MCF51AC256AVLKE@LQFP80 [DX3017]
MCF51AC256AVPUE@LQFP64 [DX3011]
MCF51AC256BCFUE@QFP64 [DX3014]
MCF51AC256BCLKE@LQFP80 [DX3017]
MCF51AC256BCPUE@LQFP64 [DX3011]
MCF51AC256BMFUE@QFP64 [DX3014]
MCF51AC256BMLKE@LQFP80 [DX3017]
MCF51AC256BMPUE@LQFP64 [DX3011]
MCF51AC256BVFUE@QFP64 [DX3014]
MCF51AC256BVLKE@LQFP80 [DX3017]
MCF51AC256BVPUE@LQFP64 [DX3011]
MCF51AC256CCFUE@QFP64 [DX3014]
MCF51AC256CCLKE@LQFP80 [DX3017]
MCF51AC256CCPUE@LQFP64 [DX3011]
MCF51AC256CMFUE@QFP64 [DX3014]
MCF51AC256CMLKE@LQFP80 [DX3017]
MCF51AC256CMPUE@LQFP64 [DX3011]
MCF51AC256CVFUE@QFP64 [DX3014]
MCF51AC256CVLKE@LQFP80 [DX3017]
MCF51AC256CVPUE@LQFP64 [DX3011]
MCF51CN128CGT@QFN48 [DX4021]
MCF51CN128CLH@LQFP64 [DX3011]
MCF51CN128CLK@LQFP80 [DX3017]
MCF51CN128MGT@QFN48 [DX4021]
MCF51CN128MLH@LQFP64 [DX3011]
MCF51CN128MLK@LQFP80 [DX3017]
MCF51CN128VGT@QFN48 [DX4021]
MCF51CN128VLH@LQFP64 [DX3011]
MCF51CN128VLK@LQFP80 [DX3017]
MCF51JE128CLK@QFP80 [DX3016]
MCF51JE128CLL@QFP100 [DX3021]
MCF51JE128MLK@QFP80 [DX3016]
MCF51JE128MLL@QFP100 [DX3021]
MCF51JE128VLK@QFP80 [DX3016]
MCF51JE128VLL@QFP100 [DX3021]
MCF51JE256CLK@QFP80 [DX3016]
MCF51JE256CLL@QFP100 [DX3021]
MCF51JE256MLK@QFP80 [DX3016]
MCF51JE256MLL@QFP100 [DX3021]
MCF51JE256VLK@QFP80 [DX3016]
MCF51JE256VLL@QFP100 [DX3021]
MCF51JM128CLD@LQFP44 [DX3005]
MCF51JM128CLH@LQFP64 [DX3011]
MCF51JM128CLK@LQFP80 [DX3017]
MCF51JM128CQH@QFP64 [DX3014]
MCF51JM128ECLK@LQFP80 [DX3017]
MCF51JM128EMLK@LQFP80 [DX3017]

MCF51JM128EVLK@LQFP80 [DX3017]
MCF51JM128MLD@LQFP44 [DX3005]
MCF51JM128MLH@LQFP64 [DX3011]
MCF51JM128MLK@LQFP80 [DX3017]
MCF51JM128MQH@QFP64 [DX3014]
MCF51JM128VLD@LQFP44 [DX3005]
MCF51JM128VLH@LQFP64 [DX3011]
MCF51JM128VLK@LQFP80 [DX3017]
MCF51JM128VQH@QFP64 [DX3014]
MCF51JM32CLD@LQFP44 [DX3005]
MCF51JM32CLH@LQFP64 [DX3011]
MCF51JM32CLK@LQFP80 [DX3017]
MCF51JM32CQH@QFP64 [DX3014]
MCF51JM32ECLK@LQFP80 [DX3017]
MCF51JM32EMLK@LQFP80 [DX3017]
MCF51JM32EVLK@LQFP80 [DX3017]
MCF51JM32MLD@LQFP44 [DX3005]
MCF51JM32MLH@LQFP64 [DX3011]
MCF51JM32MLK@LQFP80 [DX3017]
MCF51JM32MQH@QFP64 [DX3014]
MCF51JM32VLD@LQFP44 [DX3005]
MCF51JM32VLH@LQFP64 [DX3011]
MCF51JM32VLK@LQFP80 [DX3017]
MCF51JM32VQH@QFP64 [DX3014]
MCF51JM64CLD@LQFP44 [DX3005]
MCF51JM64CLH@LQFP64 [DX3011]
MCF51JM64CLK@LQFP80 [DX3017]
MCF51JM64CQH@QFP64 [DX3014]
MCF51JM64ECLK@LQFP80 [DX3017]
MCF51JM64EMLK@LQFP80 [DX3017]
MCF51JM64EVLK@LQFP80 [DX3017]
MCF51JM64MLD@LQFP44 [DX3005]
MCF51JM64MLH@LQFP64 [DX3011]
MCF51JM64MLK@LQFP80 [DX3017]
MCF51JM64MQH@QFP64 [DX3014]
MCF51JM64VLD@LQFP44 [DX3005]
MCF51JM64VLH@LQFP64 [DX3011]
MCF51JM64VLK@LQFP80 [DX3017]
MCF51JM64VQH@QFP64 [DX3014]
MCF51QE128CLH@QFP64 [DX3011]
MCF51QE128CLK@QFP80 [DX3017]
MCF51QE128LH@QFP64 [DX3011]
MCF51QE128LK@QFP80 [DX3017]
MCF51QE128MLH@QFP64 [DX3011]
MCF51QE128MLK@QFP80 [DX3017]
MCF51QE128VLH@QFP64 [DX3011]
MCF51QE128VLK@QFP80 [DX3017]
MCF51QE32CLH@QFP64 [DX3011]
MCF51QE32CLK@QFP80 [DX3017]
MCF51QE32LH@QFP64 [DX3011]
MCF51QE32LK@QFP80 [DX3017]
MCF51QE32MLH@QFP64 [DX3011]
MCF51QE32MLK@QFP80 [DX3017]
MCF51QE32VLH@QFP64 [DX3011]
MCF51QE32VLK@QFP80 [DX3017]
MCF51QE64CLH@QFP64 [DX3011]
MCF51QE64CLK@QFP80 [DX3017]
MCF51QE64LH@QFP64 [DX3011]
MCF51QE64LK@QFP80 [DX3017]
MCF51QE64MLH@QFP64 [DX3011]
MCF51QE64MLK@QFP80 [DX3017]
MCF51QE64VLH@QFP64 [DX3011]
MCF51QE64VLK@QFP80 [DX3017]
MCF51QE96CLH@QFP64 [DX3011]
MCF51QE96CLK@QFP80 [DX3017]
MCF51QE96LH@QFP64 [DX3011]
MCF51QE96LK@QFP80 [DX3017]
MCF51QE96MLH@QFP64 [DX3011]
MCF51QE96MLK@QFP80 [DX3017]
MCF51QE96VLH@QFP64 [DX3011]
MCF51QE96VLK@QFP80 [DX3017]
MCF52100CAE66@QFP64 [DX3011]
MCF52100CAE80@QFP64 [DX3011]
MCF52100CEP66@QFN64 [DX4023]
MCF52100CEP80@QFN64 [DX4023]
MCF52100LCVM66@BGA81 [DX5089]
MCF52100LCVM80@BGA81 [DX5089]
MCF52110CAE66@QFP64 [DX3011]
MCF52110CAE80@QFP64 [DX3011]
MCF52110CAF66@QFP100 [DX3021]
MCF52110CAF80@QFP100 [DX3021]
MCF52110CEP66@QFN64 [DX4023]
MCF52110CEP80@QFN64 [DX4023]
MCF52110LCVM66@BGA81 [DX5089]
MCF52110LCVM80@BGA81 [DX5089]
MCF5211CAE66@QFP64 [DX3011]
MCF5211CEP66@QFN64 [DX4023]
MCF5211LCVM66@BGA81 [DX5089]
MCF5211LCVM80@BGA81 [DX5089]
MCF5212CAE66@QFP64 [DX3011]
MCF5212LCVM66@BGA81 [DX5089]
MCF5212LCVM80@BGA81 [DX5089]
MCF5213CAF66@QFP100 [DX3021]
MCF5213CAF80@QFP100 [DX3021]
MCF5213LCVM66@BGA81 [DX5089]
MCF5213LCVM80@BGA81 [DX5089]

MCF52210CAE66@QFP64 [DX3011]
MCF52210CEP66@QFN64 [DX4023]
MCF52210CVM66@BGA81 [DX5089]
MCF52210CVM80@BGA81 [DX5089]
MCF52211CAE66@QFP64 [DX3011]
MCF52211CAF80@QFP100 [DX3021]
MCF52211CEP66@QFN64 [DX4023]
MCF52211CVM66@BGA81 [DX5089]
MCF52211CVM80@BGA81 [DX5089]
MCF52212AE50@QFP64 [DX3011]
MCF52212CAE50@QFP64 [DX3011]
MCF52213AE50@QFP64 [DX3011]
MCF52213CAE50@QFP64 [DX3011]
MCF52221CAE66@QFP64 [DX3011]
MCF52221CAE80@QFP64 [DX3011]
MCF52221CVM66@BGA81 [DX5089]
MCF52221CVM80@BGA81 [DX5089]
MCF52223CAF66@QFP100 [DX3021]
MCF52223CAF80@QFP100 [DX3021]
MCF52223CVM66@BGA81 [DX5089]
MCF52223CVM80@BGA81 [DX5089]
MCF52230CAF60@QFP80 [DX3018]
MCF52230CAL60@QFP112 [DX3026]
MCF52231CAF60@QFP80 [DX3018]
MCF52231CAL60@QFP112 [DX3026]
MCF52232AF50@QFP80 [DX3018]
MCF52232CAF50@QFP80 [DX3018]
MCF52233CAF60@QFP80 [DX3018]
MCF52233CAL60@QFP112 [DX3026]
MCF52234CAL60@QFP112 [DX3026]
MCF52234CVM60@BGA121 [DX5090]
MCF52235CAL60@QFP112 [DX3026]
MCF52235CVM60@BGA121 [DX5090]
MCF52236AF50@QFP80 [DX3018]
MCF52236CAF50@QFP80 [DX3018]
MCF52252AF80@QFP100 [DX3021]
MCF52252CAF66@QFP100 [DX3021]
MCF52254AF80@QFP100 [DX3021]
MCF52254CAF66@QFP100 [DX3021]
MCF52255CAF80@QFP100 [DX3021]
MCF52256AG80@QFP144 [DX3035]
MCF52256CAG66@QFP144 [DX3035]
MCF52258AG80@QFP144 [DX3035]
MCF52258CAG66@QFP144 [DX3035]
MCF52259CAG80@QFP144 [DX3035]
MCHC908JW32FC@TQFN48 [DX4021]
MCHC908JW32FCE@TQFN48 [DX4021]
MM908E621ACDWB@SOIC54 [DX1060]
MM908E622ACDWB@SOIC54 [DX1060]
MM908E624ACDWB@SOIC54 [DX1060]
MM908E624ACEW@SOIC54 [DX1060]
MM908E624AYEW@SOIC54 [DX1060]
MM908E625AVDWB@SOIC54 [DX1060]
MM908E625AVEK@SOIC54 [DX1060]
MM908E626AVDWB@SOIC54 [DX1060]
MM908E626AVEK@SOIC54 [DX1060]
PC56F8011VFAE@QFP32 [DX3001]
PC56F8013VFAE@QFP32 [DX3001]
PC56F8014VFAE@QFP32 [DX3001]
PC9S08SG4CSC@SOIC8 [DX1030]
PC9S08SG4CSCE@SOIC8 [DX1030]
PC9S08SG4CTG@TSSOP16 [DX1000]
PC9S08SG4CTGE@TSSOP16 [DX1000]
PC9S08SG4CTJ@TSSOP20 [DX1000]
PC9S08SG4CTJE@TSSOP20 [DX1000]
PC9S08SG4MSC@SOIC8 [DX1030]
PC9S08SG4MSCE@SOIC8 [DX1030]
PC9S08SG4MTG@TSSOP16 [DX1000]
PC9S08SG4MTGE@TSSOP16 [DX1000]
PC9S08SG4MTJ@TSSOP20 [DX1000]
PC9S08SG4MTJE@TSSOP20 [DX1000]
PC9S08SG4VSC@SOIC8 [DX1030]
PC9S08SG4VSCE@SOIC8 [DX1030]
PC9S08SG4VTG@TSSOP16 [DX1000]
PC9S08SG4VTGE@TSSOP16 [DX1000]
PC9S08SG4VTJ@TSSOP20 [DX1000]
PC9S08SG4VTJE@TSSOP20 [DX1000]
PC9S08SG8CSC@SOIC8 [DX1030]
PC9S08SG8CSCE@SOIC8 [DX1030]
PC9S08SG8CTG@TSSOP16 [DX1000]
PC9S08SG8CTGE@TSSOP16 [DX1000]
PC9S08SG8CTJ@TSSOP20 [DX1000]
PC9S08SG8CTJE@TSSOP20 [DX1000]
PC9S08SG8MSC@SOIC8 [DX1030]
PC9S08SG8MSCE@SOIC8 [DX1030]
PC9S08SG8MTG@TSSOP16 [DX1000]
PC9S08SG8MTGE@TSSOP16 [DX1000]
PC9S08SG8MTJ@TSSOP20 [DX1000]
PC9S08SG8MTJE@TSSOP20 [DX1000]
PC9S08SG8VSC@SOIC8 [DX1030]
PC9S08SG8VSCE@SOIC8 [DX1030]
PC9S08SG8VTG@TSSOP16 [DX1000]
PC9S08SG8VTGE@TSSOP16 [DX1000]
PC9S08SG8VTJ@TSSOP20 [DX1000]
PC9S08SG8VTJE@TSSOP20 [DX1000]
PC9S08SH4CFK@QFN24 [DX4012]

PC9S08SH4CFK@QFN24(auto trim) [DX4012]
PC9S08SH4CFKE@QFN24 [DX4012]
PC9S08SH4CFKE@QFN24(auto trim) [DX4012]
PC9S08SH4CPJ PC9S08SH4CPJ(auto trim)
PC9S08SH4CPJE PC9S08SH4CPJE(auto trim)
PC9S08SH4CSC@SOIC8 [DX1030]
PC9S08SH4CSC@SOIC8(auto trim) [DX1030]
PC9S08SH4CSCE@SOIC8 [DX1030]
PC9S08SH4CSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4CTG@TSSOP16 [DX1000]
PC9S08SH4CTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4CTGE@TSSOP16 [DX1000]
PC9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4CTJ@TSSOP20 [DX1000]
PC9S08SH4CTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH4CTJE@TSSOP20 [DX1000]
PC9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4CWJ@SOIC20 [DX1033]
PC9S08SH4CWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4CWJE@SOIC20 [DX1033]
PC9S08SH4CWJE@SOIC20(auto trim) [DX1033]
PC9S08SH4MFK@QFN24 [DX4012]
PC9S08SH4MFK@QFN24(auto trim) [DX4012]
PC9S08SH4MFKE@QFN24 [DX4012]
PC9S08SH4MFKE@QFN24(auto trim) [DX4012]
PC9S08SH4MPJ PC9S08SH4MPJ(auto trim)
PC9S08SH4MPJE PC9S08SH4MPJE(auto trim)
PC9S08SH4MSC@SOIC8 [DX1030]
PC9S08SH4MSC@SOIC8(auto trim) [DX1030]
PC9S08SH4MSCE@SOIC8 [DX1030]
PC9S08SH4MSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4MTG@TSSOP16 [DX1000]
PC9S08SH4MTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4MTGE@TSSOP16 [DX1000]
PC9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4MTJ@TSSOP20 [DX1000]
PC9S08SH4MTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH4MTJE@TSSOP20 [DX1000]
PC9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4MWJ@SOIC20 [DX1033]
PC9S08SH4MWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4MWJE@SOIC20 [DX1033]
PC9S08SH4MWJE@SOIC20(auto trim) [DX1033]
PC9S08SH4VFK@QFN24 [DX4012]
PC9S08SH4VFK@QFN24(auto trim) [DX4012]
PC9S08SH4VFKE@QFN24 [DX4012]
PC9S08SH4VFKE@QFN24(auto trim) [DX4012]
PC9S08SH4VPJ PC9S08SH4VPJ(auto trim)

PC9S08SH4VPJE PC9S08SH4VPJE(auto trim)
PC9S08SH4VSC@SOIC8 [DX1030]
PC9S08SH4VSC@SOIC8(auto trim) [DX1030]
PC9S08SH4VSCE@SOIC8 [DX1030]
PC9S08SH4VSCE@SOIC8(auto trim) [DX1030]
PC9S08SH4VTG@TSSOP16 [DX1000]
PC9S08SH4VTG@TSSOP16(auto trim) [DX1000]
PC9S08SH4VTGE@TSSOP16 [DX1000]
PC9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH4VTJ@TSSOP20 [DX1000]
PC9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH4VTJE@TSSOP20 [DX1000]
PC9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH4VWJ@SOIC20 [DX1033]
PC9S08SH4VWJ@SOIC20(auto trim) [DX1033]
PC9S08SH4VWJE@SOIC20 [DX1033]
PC9S08SH4VWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8CFK@QFN24 [DX4012]
PC9S08SH8CFK@QFN24(auto trim) [DX4012]
PC9S08SH8CFKE@QFN24 [DX4012]
PC9S08SH8CFKE@QFN24(auto trim) [DX4012]
PC9S08SH8CPJ PC9S08SH8CPJ(auto trim)
PC9S08SH8CPJE PC9S08SH8CPJE(auto trim)
PC9S08SH8CSC@SOIC8 [DX1030]
PC9S08SH8CSC@SOIC8(auto trim) [DX1030]
PC9S08SH8CSCE@SOIC8 [DX1030]
PC9S08SH8CSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8CTG@TSSOP16 [DX1000]
PC9S08SH8CTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8CTGE@TSSOP16 [DX1000]
PC9S08SH8CTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8CTJ@TSSOP20 [DX1000]
PC9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8CTJE@TSSOP20 [DX1000]
PC9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8CWJ@SOIC20 [DX1033]
PC9S08SH8CWJ@SOIC20(auto trim) [DX1033]
PC9S08SH8CWJE@SOIC20 [DX1033]
PC9S08SH8CWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8MFK@QFN24 [DX4012]
PC9S08SH8MFK@QFN24(auto trim) [DX4012]
PC9S08SH8MFKE@QFN24 [DX4012]
PC9S08SH8MFKE@QFN24(auto trim) [DX4012]
PC9S08SH8MPJ PC9S08SH8MPJ(auto trim)
PC9S08SH8MPJE PC9S08SH8MPJE(auto trim)
PC9S08SH8MSC@SOIC8 [DX1030]
PC9S08SH8MSC@SOIC8(auto trim) [DX1030]
PC9S08SH8MSCE@SOIC8 [DX1030]

PC9S08SH8MSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8MTG@TSSOP16 [DX1000]
PC9S08SH8MTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8MTGE@TSSOP16 [DX1000]
PC9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8MTJ@TSSOP20 [DX1000]
PC9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8MTJE@TSSOP20 [DX1000]
PC9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8MWJ@SOIC20 [DX1033]
PC9S08SH8MWJ@SOIC20(auto trim) [DX1033]
PC9S08SH8MWJE@SOIC20 [DX1033]
PC9S08SH8MWJE@SOIC20(auto trim) [DX1033]
PC9S08SH8VFK@QFN24 [DX4012]
PC9S08SH8VFK@QFN24(auto trim) [DX4012]
PC9S08SH8VFKE@QFN24 [DX4012]
PC9S08SH8VFKE@QFN24(auto trim) [DX4012]
PC9S08SH8VPJ PC9S08SH8VPJ(auto trim)
PC9S08SH8VPJE PC9S08SH8VPJE(auto trim)
PC9S08SH8VSC@SOIC8 [DX1030]
PC9S08SH8VSC@SOIC8(auto trim) [DX1030]
PC9S08SH8VSCE@SOIC8 [DX1030]
PC9S08SH8VSCE@SOIC8(auto trim) [DX1030]
PC9S08SH8VTG@TSSOP16 [DX1000]
PC9S08SH8VTG@TSSOP16(auto trim) [DX1000]
PC9S08SH8VTGE@TSSOP16 [DX1000]
PC9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
PC9S08SH8VTJ@TSSOP20 [DX1000]
PC9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
PC9S08SH8VTJE@TSSOP20 [DX1000]
PC9S08SH8VTJE@TSSOP20(auto trim) [DX1000]
PC9S08SH8VWJ@SOIC20 [DX1033]
PC9S08SH8VWJ@SOIC20(auto trim) [DX1033]
PC9S08SH8VWJE@SOIC20 [DX1033]
PC9S08SH8VWJE@SOIC20(auto trim) [DX1033]
S908QY2ACDT@TSSOP16 [DX1001]
S908QY2ACDT@TSSOP16(a-trim) [DX1001]
S908QY2ACDTE@TSSOP16 [DX1001]
S908QY2ACDTE@TSSOP16(a-trim) [DX1001]
S908QY2ACDW@SOIC16 [DX1072]
S908QY2ACDW@SOIC16(a-trim) [DX1072]
S908QY2ACDWE@SOIC16 [DX1072]
S908QY2ACDWE@SOIC16(a-trim) [DX1072]
S908QY2AMDT@TSSOP16 [DX1001]
S908QY2AMDT@TSSOP16(a-trim) [DX1001]
S908QY2AMDTE@TSSOP16 [DX1001]
S908QY2AMDTE@TSSOP16(a-trim) [DX1001]
S908QY2AMDW@SOIC16 [DX1072]

S908QY2AMDW@SOIC16(a-trim) [DX1072]
S908QY2AMDWE@SOIC16 [DX1072]
S908QY2AMDWE@SOIC16(a-trim) [DX1072]
S908QY2AVDT@TSSOP16 [DX1001]
S908QY2AVDT@TSSOP16(a-trim) [DX1001]
S908QY2AVDTE@TSSOP16 [DX1001]
S908QY2AVDTE@TSSOP16(a-trim) [DX1001]
S908QY2AVDW@SOIC16 [DX1072]
S908QY2AVDW@SOIC16(a-trim) [DX1072]
S908QY2AVDWE@SOIC16 [DX1072]
S908QY2AVDWE@SOIC16(a-trim) [DX1072]
S908QY4ACDT@TSSOP16 [DX1001]
S908QY4ACDT@TSSOP16(a-trim) [DX1001]
S908QY4ACDTE@TSSOP16 [DX1001]
S908QY4ACDTE@TSSOP16(a-trim) [DX1001]
S908QY4ACDW@SOIC16 [DX1072]
S908QY4ACDW@SOIC16(a-trim) [DX1072]
S908QY4ACDWE@SOIC16 [DX1072]
S908QY4ACDWE@SOIC16(a-trim) [DX1072]
S908QY4AMDT@TSSOP16 [DX1001]
S908QY4AMDT@TSSOP16(a-trim) [DX1001]
S908QY4AMDTE@TSSOP16 [DX1001]
S908QY4AMDTE@TSSOP16(a-trim) [DX1001]
S908QY4AMDW@SOIC16 [DX1072]
S908QY4AMDW@SOIC16(a-trim) [DX1072]
S908QY4AMDWE@SOIC16 [DX1072]
S908QY4AMDWE@SOIC16(a-trim) [DX1072]
S908QY4AVDT@TSSOP16 [DX1001]
S908QY4AVDT@TSSOP16(a-trim) [DX1001]
S908QY4AVDTE@TSSOP16 [DX1001]
S908QY4AVDTE@TSSOP16(a-trim) [DX1001]
S908QY4AVDW@SOIC16 [DX1072]
S908QY4AVDW@SOIC16(a-trim) [DX1072]
S908QY4AVDWE@SOIC16 [DX1072]
S908QY4AVDWE@SOIC16(a-trim) [DX1072]
S9S08AW16ACFT@QFN48 [DX4021]　　S9S08AW16ACLM@QFP32 [DX3001]
S9S08AW16ACLS@QFP44 [DX3003]
S9S08AW16ACLS@QFP44(*) [SA245A+B4404]
S9S08AW16AMFT@QFN48 [DX4021]　　S9S08AW16AMLM@QFP32 [DX3001]
S9S08AW16AMLS@QFP44 [DX3003]
S9S08AW16AMLS@QFP44(*) [SA245A+B4404]
S9S08AW16AVFT@QFN48 [DX4021]　　S9S08AW16AVLM@QFP32 [DX3001]
S9S08AW16AVLS@QFP44 [DX3003]
S9S08AW16AVLS@QFP44(*) [SA245A+B4404]
S9S08AW8ACFT@QFN48 [DX4021]　　S9S08AW8ACLM@QFP32 [DX3001]
S9S08AW8ACLS@QFP44 [DX3003]
S9S08AW8ACLS@QFP44(*) [SA245A+B4404]
S9S08AW8AMFT@QFN48 [DX4021]　　S9S08AW8AMLM@QFP32 [DX3001]

S9S08AW8AMLS@QFP44 [DX3003]
S9S08AW8AMLS@QFP44(*) [SA245A+B4404]
S9S08AW8AVFT@QFN48 [DX4021]
S9S08AW8AVLM@QFP32 [DX3001]
S9S08AW8AVLS@QFP44 [DX3003]
S9S08AW8AVLS@QFP44(*) [SA245A+B4404]
S9S08SG4CSC@SOIC8 [DX1030]
S9S08SG4CSCE@SOIC8 [DX1030]
S9S08SG4CTG@TSSOP16 [DX1000]
S9S08SG4CTGE@TSSOP16 [DX1000]
S9S08SG4CTJ@TSSOP20 [DX1000]
S9S08SG4CTJE@TSSOP20 [DX1000]
S9S08SG4MSC@SOIC8 [DX1030]
S9S08SG4MSCE@SOIC8 [DX1030]
S9S08SG4MTG@TSSOP16 [DX1000]
S9S08SG4MTGE@TSSOP16 [DX1000]
S9S08SG4MTJ@TSSOP20 [DX1000]
S9S08SG4MTJE@TSSOP20 [DX1000]
S9S08SG4VSC@SOIC8 [DX1030]
S9S08SG4VSCE@SOIC8 [DX1030]
S9S08SG4VTG@TSSOP16 [DX1000]
S9S08SG4VTGE@TSSOP16 [DX1000]
S9S08SG4VTJ@TSSOP20 [DX1000]
S9S08SG4VTJE@TSSOP20 [DX1000]
S9S08SG8CSC@SOIC8 [DX1030]
S9S08SG8CSCE@SOIC8 [DX1030]
S9S08SG8CTG@TSSOP16 [DX1000]
S9S08SG8CTGE@TSSOP16 [DX1000]
S9S08SG8CTJ@TSSOP20 [DX1000]
S9S08SG8CTJE@TSSOP20 [DX1000]
S9S08SG8MSC@SOIC8 [DX1030]
S9S08SG8MSCE@SOIC8 [DX1030]
S9S08SG8MTG@TSSOP16 [DX1000]
S9S08SG8MTGE@TSSOP16 [DX1000]
S9S08SG8MTJ@TSSOP20 [DX1000]
S9S08SG8MTJE@TSSOP20 [DX1000]
S9S08SG8VSC@SOIC8 [DX1030]
S9S08SG8VSCE@SOIC8 [DX1030]
S9S08SG8VTG@TSSOP16 [DX1000]
S9S08SG8VTGE@TSSOP16 [DX1000]
S9S08SG8VTJ@TSSOP20 [DX1000]
S9S08SG8VTJE@TSSOP20 [DX1000]
S9S08SH4CFK@QFN24 [DX4012]
S9S08SH4CFK@QFN24(auto trim) [DX4012]
S9S08SH4CFKE@QFN24 [DX4012]
S9S08SH4CFKE@QFN24(auto trim) [DX4012]
S9S08SH4CPJ
S9S08SH4CPJ(auto trim)
S9S08SH4CPJE
S9S08SH4CPJE(auto trim)
S9S08SH4CSC@SOIC8 [DX1030]
S9S08SH4CSC@SOIC8(auto trim) [DX1030]
S9S08SH4CSCE@SOIC8 [DX1030]
S9S08SH4CSCE@SOIC8(auto trim) [DX1030]
S9S08SH4CTG@TSSOP16 [DX1000]
S9S08SH4CTG@TSSOP16(auto trim) [DX1000]
S9S08SH4CTGE@TSSOP16 [DX1000]
S9S08SH4CTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4CTJ@TSSOP20 [DX1000]
S9S08SH4CTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4CTJE@TSSOP20 [DX1000]
S9S08SH4CTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4CWJ@SOIC20 [DX1033]
S9S08SH4CWJ@SOIC20(auto trim) [DX1033]
S9S08SH4CWJE@SOIC20 [DX1033]
S9S08SH4CWJE@SOIC20(auto trim) [DX1033]
S9S08SH4MFK@QFN24 [DX4012]
S9S08SH4MFK@QFN24(auto trim) [DX4012]
S9S08SH4MFKE@QFN24 [DX4012]

S9S08SH4MFKE@QFN24(auto trim) [DX4012]
S9S08SH4MPJ S9S08SH4MPJ(auto trim)
S9S08SH4MPJE S9S08SH4MPJE(auto trim)
S9S08SH4MSC@SOIC8 [DX1030]
S9S08SH4MSC@SOIC8(auto trim) [DX1030]
S9S08SH4MSCE@SOIC8 [DX1030]
S9S08SH4MSCE@SOIC8(auto trim) [DX1030]
S9S08SH4MTG@TSSOP16 [DX1000]
S9S08SH4MTG@TSSOP16(auto trim) [DX1000]
S9S08SH4MTGE@TSSOP16 [DX1000]
S9S08SH4MTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4MTJ@TSSOP20 [DX1000]
S9S08SH4MTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4MTJE@TSSOP20 [DX1000]
S9S08SH4MTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4MWJ@SOIC20 [DX1033]
S9S08SH4MWJ@SOIC20(auto trim) [DX1033]
S9S08SH4MWJE@SOIC20 [DX1033]
S9S08SH4MWJE@SOIC20(auto trim) [DX1033]
S9S08SH4VFK@QFN24 [DX4012]
S9S08SH4VFK@QFN24(auto trim) [DX4012]
S9S08SH4VFKE@QFN24 [DX4012]
S9S08SH4VFKE@QFN24(auto trim) [DX4012]
S9S08SH4VPJ S9S08SH4VPJ(auto trim)
S9S08SH4VPJE S9S08SH4VPJE(auto trim)
S9S08SH4VSC@SOIC8 [DX1030]
S9S08SH4VSC@SOIC8(auto trim) [DX1030]
S9S08SH4VSCE@SOIC8 [DX1030]
S9S08SH4VSCE@SOIC8(auto trim) [DX1030]
S9S08SH4VTG@TSSOP16 [DX1000]
S9S08SH4VTG@TSSOP16(auto trim) [DX1000]
S9S08SH4VTGE@TSSOP16 [DX1000]
S9S08SH4VTGE@TSSOP16(auto trim) [DX1000]
S9S08SH4VTJ@TSSOP20 [DX1000]
S9S08SH4VTJ@TSSOP20(auto trim) [DX1000]
S9S08SH4VTJE@TSSOP20 [DX1000]
S9S08SH4VTJE@TSSOP20(auto trim) [DX1000]
S9S08SH4VWJ@SOIC20 [DX1033]
S9S08SH4VWJ@SOIC20(auto trim) [DX1033]
S9S08SH4VWJE@SOIC20 [DX1033]
S9S08SH4VWJE@SOIC20(auto trim) [DX1033]
S9S08SH8CFK@QFN24 [DX4012]
S9S08SH8CFK@QFN24(auto trim) [DX4012]
S9S08SH8CFKE@QFN24 [DX4012]
S9S08SH8CFKE@QFN24(auto trim) [DX4012]
S9S08SH8CPJ S9S08SH8CPJ(auto trim)
S9S08SH8CPJE S9S08SH8CPJE(auto trim)
S9S08SH8CSC@SOIC8 [DX1030]

S9S08SH8CSC@SOIC8(auto trim) [DX1030]
S9S08SH8CSCE@SOIC8 [DX1030]
S9S08SH8CSCE@SOIC8(auto trim) [DX1030]
S9S08SH8CTG@TSSOP16 [DX1000]
S9S08SH8CTG@TSSOP16(auto trim) [DX1000]
S9S08SH8CTGE@TSSOP16 [DX1000]
S9S08SH8CTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8CTJ@TSSOP20 [DX1000]
S9S08SH8CTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8CTJE@TSSOP20 [DX1000]
S9S08SH8CTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8CWJ@SOIC20 [DX1033]
S9S08SH8CWJ@SOIC20(auto trim) [DX1033]
S9S08SH8CWJE@SOIC20 [DX1033]
S9S08SH8CWJE@SOIC20(auto trim) [DX1033]
S9S08SH8MFK@QFN24 [DX4012]
S9S08SH8MFK@QFN24(auto trim) [DX4012]
S9S08SH8MFKE@QFN24 [DX4012]
S9S08SH8MFKE@QFN24(auto trim) [DX4012]
S9S08SH8MPJ S9S08SH8MPJ(auto trim)
S9S08SH8MPJE S9S08SH8MPJE(auto trim)
S9S08SH8MSC@SOIC8 [DX1030]
S9S08SH8MSC@SOIC8(auto trim) [DX1030]
S9S08SH8MSCE@SOIC8 [DX1030]
S9S08SH8MSCE@SOIC8(auto trim) [DX1030]
S9S08SH8MTG@TSSOP16 [DX1000]
S9S08SH8MTG@TSSOP16(auto trim) [DX1000]
S9S08SH8MTGE@TSSOP16 [DX1000]
S9S08SH8MTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8MTJ@TSSOP20 [DX1000]
S9S08SH8MTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8MTJE@TSSOP20 [DX1000]
S9S08SH8MTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8MWJ@SOIC20 [DX1033]
S9S08SH8MWJ@SOIC20(auto trim) [DX1033]
S9S08SH8MWJE@SOIC20 [DX1033]
S9S08SH8MWJE@SOIC20(auto trim) [DX1033]
S9S08SH8VFK@QFN24 [DX4012]
S9S08SH8VFK@QFN24(auto trim) [DX4012]
S9S08SH8VFKE@QFN24 [DX4012]
S9S08SH8VFKE@QFN24(auto trim) [DX4012]
S9S08SH8VPJ S9S08SH8VPJ(auto trim)
S9S08SH8VPJE S9S08SH8VPJE(auto trim)
S9S08SH8VSC@SOIC8 [DX1030]
S9S08SH8VSC@SOIC8(auto trim) [DX1030]
S9S08SH8VSCE@SOIC8 [DX1030]
S9S08SH8VSCE@SOIC8(auto trim) [DX1030]
S9S08SH8VTG@TSSOP16 [DX1000]

S9S08SH8VTG@TSSOP16(auto trim) [DX1000]
S9S08SH8VTGE@TSSOP16 [DX1000]
S9S08SH8VTGE@TSSOP16(auto trim) [DX1000]
S9S08SH8VTJ@TSSOP20 [DX1000]
S9S08SH8VTJ@TSSOP20(auto trim) [DX1000]
S9S08SH8VTJE@TSSOP20 [DX1000]
S9S08SH8VTJE@TSSOP20(auto trim) [DX1000]
S9S08SH8VWJ@SOIC20 [DX1033]
S9S08SH8VWJ@SOIC20(auto trim) [DX1033]
S9S08SH8VWJE@SOIC20 [DX1033]
S9S08SH8VWJE@SOIC20(auto trim) [DX1033]
S9S12P128CFT@QFN48 [DX4021]
S9S12P128CLH@QFP64 [DX3011]
S9S12P128CQK@QFP80 [DX3018]
S9S12P128MFT@QFN48 [DX4021]
S9S12P128MLH@QFP64 [DX3011]
S9S12P128MQK@QFP80 [DX3018]
S9S12P128VFT@QFN48 [DX4021]
S9S12P128VLH@QFP64 [DX3011]
S9S12P128VQK@QFP80 [DX3018]
S9S12P32CFT@QFN48 [DX4021]
S9S12P32CLH@QFP64 [DX3011]
S9S12P32CQK@QFP80 [DX3018]
S9S12P32MFT@QFN48 [DX4021]
S9S12P32MLH@QFP64 [DX3011]
S9S12P32MQK@QFP80 [DX3018]
S9S12P32VFT@QFN48 [DX4021]
S9S12P32VLH@QFP64 [DX3011]
S9S12P32VQK@QFP80 [DX3018]
S9S12P64CFT@QFN48 [DX4021]
S9S12P64CLH@QFP64 [DX3011]
S9S12P64CQK@QFP80 [DX3018]
S9S12P64MFT@QFN48 [DX4021]
S9S12P64MLH@QFP64 [DX3011]
S9S12P64MQK@QFP80 [DX3018]
S9S12P64VFT@QFN48 [DX4021]
S9S12P64VLH@QFP64 [DX3011]
S9S12P64VQK@QFP80 [DX3018]
S9S12P96CFT@QFN48 [DX4021]
S9S12P96CLH@QFP64 [DX3011]
S9S12P96CQK@QFP80 [DX3018]
S9S12P96MFT@QFN48 [DX4021]
S9S12P96MLH@QFP64 [DX3011]
S9S12P96MQK@QFP80 [DX3018]
S9S12P96VFT@QFN48 [DX4021]
S9S12P96VLH@QFP64 [DX3011]
S9S12P96VQK@QFP80 [DX3018]
SC101161DGCFU@TQFP80 [DX3018]
SC101161DGCPV@TQFP112 [DX3026]
SC101161DGMFU@TQFP80 [DX3018]
SC101161DGMPV@TQFP112 [DX3026]
SC101161DGVFU@TQFP80 [DX3018]
SC101161DGVPV@TQFP112 [DX3026]
SC101161DJCFU@TQFP80 [DX3018]
SC101161DJCPV@TQFP112 [DX3026]
SC101161DJMFU@TQFP80 [DX3018]
SC101161DJMPV@TQFP112 [DX3026]
SC101161DJVFU@TQFP80 [DX3018]
SC101161DJVPV@TQFP112 [DX3026]
SC101161DTCFU@TQFP80 [DX3018]
SC101161DTCPV@TQFP112 [DX3026]
SC101161DTMFU@TQFP80 [DX3018]
SC101161DTMPV@TQFP112 [DX3026]
SC101161DTVFU@TQFP80 [DX3018]
SC101161DTVPV@TQFP112 [DX3026]
SC102202CFU@TQFP80 [DX3018]
SC102202CPV@TQFP112 [DX3026]
SC102202MFU@TQFP80 [DX3018]
SC102202MPV@TQFP112 [DX3026]
SC102202VFU@TQFP80 [DX3018]
SC102202VPV@TQFP112 [DX3026]
SC102203CFU@TQFP80 [DX3018]
SC102203CPV@TQFP112 [DX3026]
SC102203MFU@TQFP80 [DX3018]
SC102203MPV@TQFP112 [DX3026]
SC102203VFU@TQFP80 [DX3018]
SC102203VPV@TQFP112 [DX3026]
SC102204CFU@TQFP80 [DX3018]
SC102204CPV@TQFP112 [DX3026]
SC102204MFU@TQFP80 [DX3018]
SC102204MPV@TQFP112 [DX3026]
SC102204VFU@TQFP80 [DX3018]
SC102204VPV@TQFP112 [DX3026]
SC102205CFU@TQFP80 [DX3018]
SC102205CPV@TQFP112 [DX3026]

SC102205MFU@TQFP80 [DX3018]
SC102205MPV@TQFP112 [DX3026]
SC102205VFU@TQFP80 [DX3018]
SC102205VPV@TQFP112 [DX3026]
SC515846CFU@TQFP80 [DX3018]
SC515846CPV@TQFP112 [DX3026]
SC515846MFU@TQFP80 [DX3018]
SC515846MPV@TQFP112 [DX3026]
SC515846VFU@TQFP80 [DX3018]
SC515846VPV@TQFP112 [DX3026]
SC515847CFU@TQFP80 [DX3018]
SC515847CPV@TQFP112 [DX3026]
SC515847MFU@TQFP80 [DX3018]
SC515847MPV@TQFP112 [DX3026]
SC515847VFU@TQFP80 [DX3018]
SC515847VPV@TQFP112 [DX3026]
SC515848CFU@TQFP80 [DX3018]
SC515848CPV@TQFP112 [DX3026]
SC515848MFU@TQFP80 [DX3018]
SC515848MPV@TQFP112 [DX3026]
SC515848VFU@TQFP80 [DX3018]
SC515848VPV@TQFP112 [DX3026]
SC515849CFU@TQFP80 [DX3018]
SC515849CPV@TQFP112 [DX3026]
SC515849MFU@TQFP80 [DX3018]
SC515849MPV@TQFP112 [DX3026]
SC515849VFU@TQFP80 [DX3018]
SC515849VPV@TQFP112 [DX3026]
XC68HC705P6A(CDW)@SOIC28 [DX1033]
XC68HC711D3 [DX0001]
XC68HC711D3(3V) [DX0001]
XC68HC711D3(3V)@PLCC44 [DX2044]
XC68HC711D3(3V)@TQFP44 [DX3002]
XC68HC711D3@PLCC44 [DX2044]
XC68HC711D3@TQFP44 [DX3002]
XC68HSC705C9A [DX0001]
XC68HSC705C9A@PLCC44 [DX2044]
XC68HSC705C9A@TQFP44 [DX3002]

MShine

E(E)PROM/FRAM/NVRAM

MS25X10 [DX0001]
MS25X10@SOP8 [DX1045]
MS25X10@TSSOP8 [DX1059]
MS25X16 [DX0001#1]
MS25X16@SOP16 [DX1072#1]
MS25X16@SOP8 [DX1044#1]
MS25X20 [DX0001]
MS25X20@SOP8 [DX1045]
MS25X20@TSSOP8 [DX1059]
MS25X32 [DX0001]
MS25X32@SOP16 [DX1072#1]
MS25X32@SOP8 [DX1044#1]
MS25X40 [DX0001]
MS25X40@SOP8 [DX1045]
MS25X512 [DX0001]
MS25X512@SOP8 [DX1045]
MS25X512@TSSOP8 [DX1059]
MS25X80 [DX0001]
MS25X80@SOP8 [DX1045]

MT

MICROCONTROLLER

LPC2141FBD64 [DX3011-8]
LPC2142FBD64 [DX3011-8]
LPC2144FBD64 [DX3011-8]
LPC2146FBD64 [DX3011-8]
LPC2148FBD64 [DX3011-8]
LPC2361FET100 [DX5055]
LPC2362FET100 [DX5055]
LPC2364@QFP100 [DX3021-4]
LPC2364FET100 [DX5055]
LPC2364FET100N [DX5055]
LPC2365FET100 [DX5055]
LPC2366@QFP100 [DX3021-4]

LPC2366FET100 [DX5055]
LPC2366FET100N [DX5055]
LPC2367FET100 [DX5055]
LPC2368@QFP100 [DX3021-4]
LPC2368FET100 [DX5055]
LPC2368FET100N [DX5055]
LPC2377@QFP144 [DX3035-4]
LPC2378@QFP144 [DX3035-4]
LPC2378N@QFP144 [DX3035-4]
LPC2387FET100 [DX5055]
LPC2388@QFP144 [DX3035-4]
P89C668 [DX0001]
P89C668@PLCC44 [DX2044]
P89C668@TQFP44 [DX3002]

MXIC

E(E)PROM/FRAM/NVRAM

MX30LF1208AA@FBGA63 [DX5046]
MX30LF1208AA@TSOP48 [DX1004-3]
MX30LF1G08AA@FBGA63 [DX5046]
MX30LF1G08AA@TSOP48 [DX1004-3]
MX30LF1G18AC@TSOP48 [DX1004-3]
MX30LF4G28AB-TI@TSOP48 [DX1004-3]

MXIC-CUSTOMER

E(E)PROM/FRAM/NVRAM

MX30LF1G08AA(JiuZhou)@TSOP48 [DX1004-1]

MY-MS

E(E)PROM/FRAM/NVRAM

MM24C01-2/3@SOIC8 [DX1045]
MM24C01-3 [DX0001]
MM24C01-3@SOIC8 [DX1045]
MM24C02-2/3@SOIC8 [DX1045]
MM24C02-3 [DX0001]
MM24C02-3@SOIC8 [DX1045]
MM24C04-2/3@SOIC8 [DX1045]
MM24C04-3 [DX0001]
MM24C04-3@SOIC8 [DX1045]
MM24C08-2/3@SOIC8 [DX1045]
MM24C08-3 [DX0001]
MM24C08-3@SOIC8 [DX1045]
MM24C16-2/3@SOIC8 [DX1045]
MM24C16-3 [DX0001]
MM24C16-3@SOIC8 [DX1045]

MYSON

MICROCONTROLLER

CS8954F@PQFP44 [DX3002]
CS8954N [DX0001]
CS8954V@PLCC44 [DX2044]
CS8955F@PQFP44 [DX3002]
CS8955G@LQFP48 [DX3007]
CS8955HF@PQFP44 [DX3002]
CS8955HG@LQFP48 [DX3007]
CS8955HN [DX0001]
CS8955HV@PLCC44 [DX2044]
CS8955N [DX0001]

CS8955V@PLCC44 [DX2044]
MTV212MN32 [DX0001]
MTV212MN64I [DX0001]
MTV212MS32@SDIP42 [DX0042]
MTV212MS64I@SDIP42 [DX0042]
MTV212MV32@PLCC44 [DX2044]
MTV212MV64I@PLCC44 [DX2044]
MTV230GMF@TQFP44 [DX3002]
MTV230GMS@SDIP42 [DX0042]
MTV230GMV@PLCC44 [DX2044]
MTV230MF@TQFP44 [DX3002]
MTV230MS@SDIP42 [DX0042]
MTV230MV@PLCC44 [DX2044]
MTV230PMF@TQFP44 [DX3002]
MTV230PMS@SDIP42 [DX0042]
MTV230PMV@PLCC44 [DX2044]
MTV312MN64(AG VERSION) [DX0001]
MTV312MN64(AJ VERSION) [DX0001]
MTV312MS64(AG VERSION)@SDIP42 [DX0042]
MTV312MS64(AJ VERSION)@SDIP42 [DX0042]
MTV312MV64(AG VERSION)@PLCC44 [DX2044]
MTV312MV64(AJ VERSION)@PLCC44 [DX2044]
MTV412MF128@PQFP44 [DX3002]
MTV412MS128@SDIP42 [DX0042]
MTV412MV128@PLCC44 [DX2044]
MTV416GMF@TQFP44 [DX3002]
MTV416GMG@TQFP48 [DX3007]
MTV416GMV@PLCC44 [DX2044]
MTV416MF@TQFP44 [DX3002]
MTV416MG@TQFP48 [DX3007]
MTV416MV@PLCC44 [DX2044]
MTV416PMF@TQFP44 [DX3002]
MTV416PMG@TQFP48 [DX3007]
MTV416PMV@PLCC44 [DX2044]
MTV512MF(A1 VERSION)@TQFP44 [DX3002]
MTV512MF(A3 VERSION)@TQFP44 [DX3002]
MTV512MV(A1 VERSION)@PLCC44 [DX2044]
MTV512MV(A3 VERSION)@PLCC44 [DX2044]

NAMUGA

E(E)PROM/FRAM/NVRAM

EN25Q40@USON8 [DX4005#1]
GD25Q20@USON8 [DX4047#1]
GD25Q20B@USON8 [DX4047#1]
GD25Q512-U08 [DX4047#1]

NANOIC

MICROCONTROLLER

WN2108@SOIC14 [DX1016]

NANSI

E(E)PROM/FRAM/NVRAM

N25S10 [DX0001]
N25S10@SOP8 [DX1045#1]
N25S10@VDFN8 [DX4005#1]
N25S16 [DX0001#1]
N25S16@SOIC16 [DX1072#1]
N25S16@SOIC8 [DX1044#1]
N25S16@WSON8 [DX4005#1]
N25S20 [DX0001]

N25S20@SOP8 [DX1045#1]
N25S20@VDFN8 [DX4005#1]
N25S32 [DX0001#1]
N25S32@SOIC16 [DX1072#1]
N25S32@SOIC8 [DX1044#1]
N25S32@WSON8 [DX4005#1]
N25S40 [DX0001]
N25S40@SOIC8[150mil] [DX1045#1]
N25S40@SOIC8[200mil] [DX1044#1]
N25S40@WSON8 [DX4005#1]
N25S80 [DX0001#1]
N25S80@SOP16 [DX1072#1]
N25S80@SOP8 [DX1044#1]
N25S80@VDFN8 [DX4005#1]

NANTRONICS

E(E)PROM/FRAM/NVRAM

N25S32 [DX0001#1]
N25S32@SOIC16 [DX1072#1]
N25S32@SOIC8 [DX1044#1]
N25S32@WSON8 [DX4005#1]
N25S80 [DX0001]
N25S80@SOIC8[150mil] [DX1045#1]
N25S80@SOIC8[200mil] [DX1044#1]
N25S80@WSON8 [DX4005#1]

NANYA

E(E)PROM/FRAM/NVRAM

NT5SV16M16BS@TSOP54 [DX1010]

NATRONICS

E(E)PROM/FRAM/NVRAM

NS29LV032FB@FBGA48 [DX5002]
NS29LV032FB@TSOP48 [DX1004]
NS29LV032FT@FBGA48 [DX5002]
NS29LV032FT@TSOP48 [DX1004]

NEC

E(E)PROM/FRAM/NVRAM

D2716D [DX0001]
uPD271000 [DX0001]
uPD271000@PLCC32 [DX2032]
uPD271000@TSOP32 [DX1002]
uPD27128 [DX0001]
uPD27128(C) [DX0001]
uPD27128(D) [DX0001]
uPD2716 [DX0001]
uPD27256 [DX0001]
uPD27256(C) [DX0001]
uPD27256(D) [DX0001]
uPD27256A [DX0001]
uPD27256A(C) [DX0001]
uPD27256A(D) [DX0001]
uPD2732 [DX0001]
uPD2732A [DX0001]
uPD27512 [DX0001]
uPD27512ACT [DX0001]
uPD27512AD [DX0001]
uPD2764 [DX0001]
uPD2764C [DX0001]
uPD2764D [DX0001]

uPD27C1000 [DX0001]
uPD27C1000@PLCC32 [DX2032]
uPD27C1000@TSOP32 [DX1002]
uPD27C1000A [DX0001]
uPD27C1000A@PLCC32 [DX2032]
uPD27C1000A@TSOP32 [DX1002]
uPD27C1000AD [DX0001]
uPD27C1000AD@PLCC32 [DX2032]
uPD27C1000AD@TSOP32 [DX1002]
uPD27C1001 [DX0001]
uPD27C1001@PLCC32 [DX2032]
uPD27C1001@TSOP32 [DX1002]
uPD27C1001A [DX0001]
uPD27C1001A@PLCC32 [DX2032]
uPD27C1001A@TSOP32 [DX1002]
uPD27C1001D [DX0001]
uPD27C1001D@PLCC32 [DX2032]
uPD27C1001D@TSOP32 [DX1002]
uPD27C1024 [DX0001]
uPD27C1024A [DX0001]
uPD27C2001 [DX0001]
uPD27C2001@PLCC32 [DX2032]
uPD27C2001@TSOP32 [DX1002]
uPD27C2001D [DX0001]
uPD27C2001D@PLCC32 [DX2032]
uPD27C2001D@TSOP32 [DX1002]
uPD27C210 [DX0001]
uPD27C256 [DX0001]
uPD27C256A [DX0001]
uPD27C400 [DX0001]
uPD27C4001 [DX0001]
uPD27C4001@PLCC32 [DX2032]
uPD27C4001@TSOP32 [DX1002]
uPD27C4096 [DX0001]
uPD27C512 [DX0001]
uPD27C64(C) [DX0001]
uPD27C64(D) [DX0001]
uPD27C8000 [DX0001]
uPD27C8001 [DX0001]
uPD27C8001@PLCC32 [DX2032]
uPD27C8001@TSOP32 [DX1002]
uPD28C04 [DX0001]
uPD28C04@SOIC24 [DX1033]
uPD28C05 [DX0001]
uPD28C05@SOIC24 [DX1033]
uPD28C256 [DX0001]
uPD28C64 [DX0001]
uPD28C64@SOIC28 [DX1033]
uPD29F008CB@TSOP40 [DX1006]
uPD29F008CT@TSOP40 [DX1006]

MICROCONTROLLER

R5F1006AASP [DX1026]
R5F1006ADSP [DX1026]
R5F1006CASP [DX1026]
R5F1006CDSP [DX1026]
R5F1006DASP [DX1026]
R5F1006DDSP [DX1026]
R5F1006EASP [DX1026]
R5F1006EDSP [DX1026]
R5F1006FASP [DX1026]
R5F1006FDSP [DX1026]
R5F1006GASP [DX1026]
R5F1006GDSP [DX1026]
R5F1006HASP [DX1026]
R5F1006HDSP [DX1026]
R5F1006JASP [DX1026]
R5F1006JDSP [DX1026]
R5F1006KASP [DX1026]
R5F1006KDSP [DX1026]
R5F1006LASP [DX1026]
R5F1006LDSP [DX1026]
R5F1007AANA [DX4012]
R5F1007ADNA [DX4012]
R5F1007CANA [DX4012]
R5F1007CDNA [DX4012]
R5F1007DANA [DX4012]
R5F1007DDNA [DX4012]
R5F1007EANA [DX4012]
R5F1007EDNA [DX4012]
R5F1007FANA [DX4012]
R5F1007FDNA [DX4012]
R5F1007GANA [DX4012]
R5F1007GDNA [DX4012]
R5F1007HANA [DX4012]
R5F1007HDNA [DX4012]
R5F1007JANA [DX4012]
R5F1007JDNA [DX4012]
R5F1007KANA [DX4012]
R5F1007KDNA [DX4012]

R5F1007LANA [DX4012]
R5F1007LDNA [DX4012]
R5F1008AALA [DX0001]
R5F1008ADLA [DX0001]
R5F1008CALA [DX0001]
R5F1008CDLA [DX0001]
R5F1008DALA [DX0001]
R5F1008DDLA [DX0001]
R5F1008EALA [DX0001]
R5F1008EDLA [DX0001]
R5F1008FALA [DX0001]
R5F1008FDLA [DX0001]
R5F1008GALA [DX0001]
R5F1008GDLA [DX0001]
R5F1008HALA [DX0001]
R5F1008HDLA [DX0001]
R5F1008JALA [DX0001]
R5F1008JDLA [DX0001]
R5F1008KALA [DX0001]
R5F1008KDLA [DX0001]
R5F1008LALA [DX0001]
R5F1008LDLA [DX0001]
R5F100AAASP [DX1027]
R5F100AADSP [DX1027]
R5F100ACASP [DX1027]
R5F100ACDSP [DX1027]
R5F100ADASP [DX1027]
R5F100ADDSP [DX1027]
R5F100AEASP [DX1027]
R5F100AEDSP [DX1027]
R5F100AFASP [DX1027]
R5F100AFDSP [DX1027]
R5F100AGASP [DX1027]
R5F100AGDSP [DX1027]
R5F100AHASP [DX1027]
R5F100AHDSP [DX1027]
R5F100AJASP [DX1027]
R5F100AJDSP [DX1027]
R5F100AKASP [DX1027]
R5F100AKDSP [DX1027]
R5F100ALASP [DX1027]
R5F100ALDSP [DX1027]
R5F100BAANA [DX4015]
R5F100BADNA [DX4015]
R5F100BCANA [DX4015]
R5F100BCDNA [DX4015]
R5F100BDANA [DX4015]
R5F100BDDNA [DX4015]
R5F100BEANA [DX4015]
R5F100BEDNA [DX4015]
R5F100BFANA [DX4015]
R5F100BFDNA [DX4015]
R5F100BGANA [DX4015]
R5F100BGDNA [DX4015]
R5F100BHANA [DX4015]
R5F100BHDNA [DX4015]
R5F100BJANA [DX4015]
R5F100BJDNA [DX4015]
R5F100BKANA [DX4015]
R5F100BKDNA [DX4015]
R5F100BLANA [DX4015]
R5F100BLDNA [DX4015]
R5F100CAALA [DX0001]
R5F100CADLA [DX0001]
R5F100CCALA [DX0001]
R5F100CCDLA [DX0001]
R5F100CDALA [DX0001]
R5F100CDDLA [DX0001]
R5F100CEALA [DX0001]
R5F100CEDLA [DX0001]
R5F100CFALA [DX0001]
R5F100CFDLA [DX0001]
R5F100CGALA [DX0001]
R5F100CGDLA [DX0001]
R5F100CHALA [DX0001]
R5F100CHDLA [DX0001]
R5F100CJALA [DX0001]
R5F100CJDLA [DX0001]
R5F100CKALA [DX0001]
R5F100CKDLA [DX0001]
R5F100CLALA [DX0001]
R5F100CLDLA [DX0001]
R5F100EAANA [DX4017]
R5F100EADNA [DX4017]
R5F100ECANA [DX4017]
R5F100ECDNA [DX4017]
R5F100EDANA [DX4017]
R5F100EDDNA [DX4017]
R5F100EEANA [DX4017]
R5F100EEDNA [DX4017]
R5F100EFANA [DX4017]
R5F100EFDNA [DX4017]
R5F100EGANA [DX4017]
R5F100EGDNA [DX4017]
R5F100EHANA [DX4017]
R5F100EHDNA [DX4017]

R5F100EJANA [DX4017]
R5F100EJDNA [DX4017]
R5F100EKANA [DX4017]
R5F100EKDNA [DX4017]
R5F100ELANA [DX4017]
R5F100ELDNA [DX4017]
R5F100FAAFP [DX3005]
R5F100FADFP [DX3005]
R5F100FCAFP [DX3005]
R5F100FCDFP [DX3005]
R5F100FDAFP [DX3005]
R5F100FDDFP [DX3005]
R5F100FEAFP [DX3005]
R5F100FEDFP [DX3005]
R5F100FFAFP [DX3005]
R5F100FFDFP [DX3005]
R5F100FGAFP [DX3005]
R5F100FGDFP [DX3005]
R5F100FHAFP [DX3005]
R5F100FHDFP [DX3005]
R5F100FJAFP [DX3005]
R5F100FJDFP [DX3005]
R5F100FKAFP [DX3005]
R5F100FKDFP [DX3005]
R5F100FLAFP [DX3005]
R5F100FLDFP [DX3005]
R5F100GAAFB [DX3007]
R5F100GAANA [DX4021]
R5F100GADFB [DX3007]
R5F100GADNA [DX4021]
R5F100GCAFB [DX3007]
R5F100GCANA [DX4021]
R5F100GCDFB [DX3007]
R5F100GCDNA [DX4021]
R5F100GDAFB [DX3007]
R5F100GDANA [DX4021]
R5F100GDDFB [DX3007]
R5F100GDDNA [DX4021]
R5F100GEAFB [DX3007]
R5F100GEANA [DX4021]
R5F100GEDFB [DX3007]
R5F100GEDNA [DX4021]
R5F100GFAFB [DX3007]
R5F100GFANA [DX4021]
R5F100GFDFB [DX3007]
R5F100GFDNA [DX4021]
R5F100GGAFB [DX3007]
R5F100GGANA [DX4021]
R5F100GGDFB [DX3007]
R5F100GGDNA [DX4021]
R5F100GHAFB [DX3007]
R5F100GHANA [DX4021]
R5F100GHDFB [DX3007]
R5F100GHDNA [DX4021]
R5F100GJAFB [DX3007]
R5F100GJANA [DX4021]
R5F100GJDFB [DX3007]
R5F100GJDNA [DX4021]
R5F100GKAFB [DX3007]
R5F100GKANA [DX4021]
R5F100GKDFB [DX3007]
R5F100GKDNA [DX4021]
R5F100GLAFB [DX3007]
R5F100GLANA [DX4021]
R5F100GLDFB [DX3007]
R5F100GLDNA [DX4021]
R5F100JCAFA [DX3010]
R5F100JCDFA [DX3010]
R5F100JDAFA [DX3010]
R5F100JDDFA [DX3010]
R5F100JEAFA [DX3010]
R5F100JEDFA [DX3010]
R5F100JFAFA [DX3010]
R5F100JFDFA [DX3010]
R5F100JGAFA [DX3010]
R5F100JGDFA [DX3010]
R5F100JHAFA [DX3010]
R5F100JHDFA [DX3010]
R5F100JJAFA [DX3010]
R5F100JJDFA [DX3010]
R5F100JKAFA [DX3010]
R5F100JKDFA [DX3010]
R5F100JLAFA [DX3010]
R5F100JLDFA [DX3010]
R5F100LCABG [DX0001]
R5F100LCAFA [DX3012]
R5F100LCAFB [DX3011]
R5F100LCAFC [DX3085]
R5F100LCDBG [DX0001]
R5F100LCDFA [DX3012]
R5F100LCDFB [DX3011]
R5F100LCDFC [DX3085]
R5F100LDABG [DX0001]
R5F100LDAFA [DX3012]
R5F100LDAFB [DX3011]
R5F100LDAFC [DX3085]

R5F100LDDBG [DX0001]
R5F100LDDFA [DX3012]
R5F100LDDFB [DX3011]
R5F100LDDFC [DX3085]
R5F100LEABG [DX0001]
R5F100LEAFA [DX3012]
R5F100LEAFB [DX3011]
R5F100LEAFC [DX3085]
R5F100LEDBG [DX0001]
R5F100LEDFA [DX3012]
R5F100LEDFB [DX3011]
R5F100LEDFC [DX3085]
R5F100LFABG [DX0001]
R5F100LFAFA [DX3012]
R5F100LFAFB [DX3011]
R5F100LFAFC [DX3085]
R5F100LFDBG [DX0001]
R5F100LFDFA [DX3012]
R5F100LFDFB [DX3011]
R5F100LFDFC [DX3085]
R5F100LGABG [DX0001]
R5F100LGAFA [DX3012]
R5F100LGAFB [DX3011]
R5F100LGAFC [DX3085]
R5F100LGDBG [DX0001]
R5F100LGDFA [DX3012]
R5F100LGDFB [DX3011]
R5F100LGDFC [DX3085]
R5F100LHABG [DX0001]
R5F100LHAFA [DX3012]
R5F100LHAFB [DX3011]
R5F100LHAFC [DX3085]
R5F100LHDBG [DX0001]
R5F100LHDFA [DX3012]
R5F100LHDFB [DX3011]
R5F100LHDFC [DX3085]
R5F100LJABG [DX0001]
R5F100LJAFA [DX3012]
R5F100LJAFB [DX3011]
R5F100LJAFC [DX3085]
R5F100LJDBG [DX0001]
R5F100LJDFA [DX3012]
R5F100LJDFB [DX3011]
R5F100LJDFC [DX3085]
R5F100LKABG [DX0001]
R5F100LKAFA [DX3012]
R5F100LKAFB [DX3011]
R5F100LKAFC [DX3085]
R5F100LKDBG [DX0001]
R5F100LKDFA [DX3012]
R5F100LKDFB [DX3011]
R5F100LKDFC [DX3085]
R5F100LLABG [DX0001]
R5F100LLAFA [DX3012]
R5F100LLAFB [DX3011]
R5F100LLAFC [DX3085]
R5F100LLDBG [DX0001]
R5F100LLDFA [DX3012]
R5F100LLDFB [DX3011]
R5F100LLDFC [DX3085]
R5F100MCAFA [DX3017]
R5F100MCAFB [DX3016]
R5F100MCDFA [DX3017]
R5F100MCDFB [DX3016]
R5F100MDAFA [DX3017]
R5F100MDAFB [DX3016]
R5F100MDDFA [DX3017]
R5F100MDDFB [DX3016]
R5F100MEAFA [DX3017]
R5F100MEAFB [DX3016]
R5F100MEDFA [DX3017]
R5F100MEDFB [DX3016]
R5F100MFAFA [DX3017]
R5F100MFAFB [DX3016]
R5F100MFDFA [DX3017]
R5F100MFDFB [DX3016]
R5F100MGAFA [DX3017]
R5F100MGAFB [DX3016]
R5F100MGDFA [DX3017]
R5F100MGDFB [DX3016]
R5F100MHAFA [DX3017]
R5F100MHAFB [DX3016]
R5F100MHDFA [DX3017]
R5F100MHDFB [DX3016]
R5F100MJAFA [DX3017]
R5F100MJAFB [DX3016]
R5F100MJDFA [DX3017]
R5F100MJDFB [DX3016]
R5F100MKAFA [DX3017]
R5F100MKAFB [DX3016]
R5F100MKDFA [DX3017]
R5F100MKDFB [DX3016]
R5F100MLAFA [DX3017]
R5F100MLAFB [DX3016]
R5F100MLDFA [DX3017]
R5F100MLDFB [DX3016]

R5F100PCAFA [DX3062]
R5F100PCDFA [DX3062]
R5F100PDAFA [DX3062]
R5F100PDDFA [DX3062]
R5F100PEAFA [DX3062]
R5F100PEDFA [DX3062]
R5F100PFAFA [DX3062]
R5F100PFDFA [DX3062]
R5F100PGAFA [DX3062]
R5F100PGDFA [DX3062]
R5F100PHAFA [DX3062]
R5F100PHDFA [DX3062]
R5F100PJAFA [DX3062]
R5F100PJDFA [DX3062]
R5F100PKAFA [DX3062]
R5F100PKDFA [DX3062]
R5F100PLAFA [DX3062]
R5F100PLDFA [DX3062]
R5F100SCAFB [DX3031]
R5F100SDAFB [DX3031]
R5F100SEAFB [DX3031]
R5F100SFAFB [DX3031]
R5F100SGAFB [DX3031]
R5F100SHAFB [DX3031]
R5F100SJAFB [DX3031]
R5F100SKAFB [DX3031]
R5F100SLAFB [DX3031]
R5F1016AASP [DX1026]
R5F1016CASP [DX1026]
R5F1016DASP [DX1026]
R5F1016EASP [DX1026]
R5F1016FASP [DX1026]
R5F1016GASP [DX1026]
R5F1016HASP [DX1026]
R5F1016JASP [DX1026]
R5F1016KASP [DX1026]
R5F1016LASP [DX1026]
R5F1017AANA [DX4012]
R5F1017CANA [DX4012]
R5F1017DANA [DX4012]
R5F1017EANA [DX4012]
R5F1017FANA [DX4012]
R5F1017GANA [DX4012]
R5F1017HANA [DX4012]
R5F1017JANA [DX4012]
R5F1017KANA [DX4012]
R5F1017LANA [DX4012]
R5F1018AALA [DX0001]
R5F100PCAFB [DX3021]
R5F100PCDFB [DX3021]
R5F100PDAFB [DX3021]
R5F100PDDFB [DX3021]
R5F100PEAFB [DX3021]
R5F100PEDFB [DX3021]
R5F100PFAFB [DX3021]
R5F100PFDFB [DX3021]
R5F100PGAFB [DX3021]
R5F100PGDFB [DX3021]
R5F100PHAFB [DX3021]
R5F100PHDFB [DX3021]
R5F100PJAFB [DX3021]
R5F100PJDFB [DX3021]
R5F100PKAFB [DX3021]
R5F100PKDFB [DX3021]
R5F100PLAFB [DX3021]
R5F100PLDFB [DX3021]
R5F100SCDFB [DX3031]
R5F100SDDFB [DX3031]
R5F100SEDFB [DX3031]
R5F100SFDFB [DX3031]
R5F100SGDFB [DX3031]
R5F100SHDFB [DX3031]
R5F100SJDFB [DX3031]
R5F100SKDFB [DX3031]
R5F100SLDFB [DX3031]
R5F1016ADSP [DX1026]
R5F1016CDSP [DX1026]
R5F1016DDSP [DX1026]
R5F1016EDSP [DX1026]
R5F1016FDSP [DX1026]
R5F1016GDSP [DX1026]
R5F1016HDSP [DX1026]
R5F1016JDSP [DX1026]
R5F1016KDSP [DX1026]
R5F1016LDSP [DX1026]
R5F1017ADNA [DX4012]
R5F1017CDNA [DX4012]
R5F1017DDNA [DX4012]
R5F1017EDNA [DX4012]
R5F1017FDNA [DX4012]
R5F1017GDNA [DX4012]
R5F1017HDNA [DX4012]
R5F1017JDNA [DX4012]
R5F1017KDNA [DX4012]
R5F1017LDNA [DX4012]
R5F1018ADLA [DX0001]

R5F1018CALA [DX0001]
R5F1018CDLA [DX0001]
R5F1018DALA [DX0001]
R5F1018DDLA [DX0001]
R5F1018EALA [DX0001]
R5F1018EDLA [DX0001]
R5F1018FALA [DX0001]
R5F1018FDLA [DX0001]
R5F1018GALA [DX0001]
R5F1018GDLA [DX0001]
R5F1018HALA [DX0001]
R5F1018HDLA [DX0001]
R5F1018JALA [DX0001]
R5F1018JDLA [DX0001]
R5F1018KALA [DX0001]
R5F1018KDLA [DX0001]
R5F1018LALA [DX0001]
R5F1018LDLA [DX0001]
R5F101AAASP [DX1027]
R5F101AADSP [DX1027]
R5F101ACASP [DX1027]
R5F101ACDSP [DX1027]
R5F101ADASP [DX1027]
R5F101ADDSP [DX1027]
R5F101AEASP [DX1027]
R5F101AEDSP [DX1027]
R5F101AFASP [DX1027]
R5F101AFDSP [DX1027]
R5F101AGASP [DX1027]
R5F101AGDSP [DX1027]
R5F101AHASP [DX1027]
R5F101AHDSP [DX1027]
R5F101AJASP [DX1027]
R5F101AJDSP [DX1027]
R5F101AKASP [DX1027]
R5F101AKDSP [DX1027]
R5F101ALASP [DX1027]
R5F101ALDSP [DX1027]
R5F101BAANA [DX4015]
R5F101BADNA [DX4015]
R5F101BCANA [DX4015]
R5F101BCDNA [DX4015]
R5F101BDANA [DX4015]
R5F101BDDNA [DX4015]
R5F101BEANA [DX4015]
R5F101BEDNA [DX4015]
R5F101BFANA [DX4015]
R5F101BFDNA [DX4015]
R5F101BGANA [DX4015]
R5F101BGDNA [DX4015]
R5F101BHANA [DX4015]
R5F101BHDNA [DX4015]
R5F101BJANA [DX4015]
R5F101BJDNA [DX4015]
R5F101BKANA [DX4015]
R5F101BKDNA [DX4015]
R5F101BLANA [DX4015]
R5F101BLDNA [DX4015]
R5F101CAALA [DX0001]
R5F101CADLA [DX0001]
R5F101CCALA [DX0001]
R5F101CCDLA [DX0001]
R5F101CDALA [DX0001]
R5F101CDDLA [DX0001]
R5F101CEALA [DX0001]
R5F101CEDLA [DX0001]
R5F101CFALA [DX0001]
R5F101CFDLA [DX0001]
R5F101CGALA [DX0001]
R5F101CGDLA [DX0001]
R5F101CHALA [DX0001]
R5F101CHDLA [DX0001]
R5F101CJALA [DX0001]
R5F101CJDLA [DX0001]
R5F101CKALA [DX0001]
R5F101CKDLA [DX0001]
R5F101CLALA [DX0001]
R5F101CLDLA [DX0001]
R5F101EAANA [DX4017]
R5F101EADNA [DX4017]
R5F101ECANA [DX4017]
R5F101ECDNA [DX4017]
R5F101EDANA [DX4017]
R5F101EDDNA [DX4017]
R5F101EEANA [DX4017]
R5F101EEDNA [DX4017]
R5F101EFANA [DX4017]
R5F101EFDNA [DX4017]
R5F101EGANA [DX4017]
R5F101EGDNA [DX4017]
R5F101EHANA [DX4017]
R5F101EHDNA [DX4017]
R5F101EJANA [DX4017]
R5F101EJDNA [DX4017]
R5F101EKANA [DX4017]
R5F101EKDNA [DX4017]

R5F101ELANA [DX4017]
R5F101ELDNA [DX4017]
R5F101FAAFP [DX3005]
R5F101FADFP [DX3005]
R5F101FCAFP [DX3005]
R5F101FCDFP [DX3005]
R5F101FDAFP [DX3005]
R5F101FDDFP [DX3005]
R5F101FEAFP [DX3005]
R5F101FEDFP [DX3005]
R5F101FFAFP [DX3005]
R5F101FFDFP [DX3005]
R5F101FGAFP [DX3005]
R5F101FGDFP [DX3005]
R5F101FHAFP [DX3005]
R5F101FHDFP [DX3005]
R5F101FJAFP [DX3005]
R5F101FJDFP [DX3005]
R5F101FKAFP [DX3005]
R5F101FKDFP [DX3005]
R5F101FLAFP [DX3005]
R5F101FLDFP [DX3005]
R5F101GAAFB [DX3007]
R5F101GAANA [DX4021]
R5F101GADFB [DX3007]
R5F101GADNA [DX4021]
R5F101GCAFB [DX3007]
R5F101GCANA [DX4021]
R5F101GCDFB [DX3007]
R5F101GCDNA [DX4021]
R5F101GDAFB [DX3007]
R5F101GDANA [DX4021]
R5F101GDDFB [DX3007]
R5F101GDDNA [DX4021]
R5F101GEAFB [DX3007]
R5F101GEANA [DX4021]
R5F101GEDFB [DX3007]
R5F101GEDNA [DX4021]
R5F101GFAFB [DX3007]
R5F101GFANA [DX4021]
R5F101GFDFB [DX3007]
R5F101GFDNA [DX4021]
R5F101GGAFB [DX3007]
R5F101GGANA [DX4021]
R5F101GGDFB [DX3007]
R5F101GGDNA [DX4021]
R5F101GHAFB [DX3007]
R5F101GHANA [DX4021]
R5F101GHDFB [DX3007]
R5F101GHDNA [DX4021]
R5F101GJAFB [DX3007]
R5F101GJANA [DX4021]
R5F101GJDFB [DX3007]
R5F101GJDNA [DX4021]
R5F101GKAFB [DX3007]
R5F101GKANA [DX4021]
R5F101GKDFB [DX3007]
R5F101GKDNA [DX4021]
R5F101GLAFB [DX3007]
R5F101GLANA [DX4021]
R5F101GLDFB [DX3007]
R5F101GLDNA [DX4021]
R5F101JCAFA [DX3010]
R5F101JCDFA [DX3010]
R5F101JDAFA [DX3010]
R5F101JDDFA [DX3010]
R5F101JEAFA [DX3010]
R5F101JEDFA [DX3010]
R5F101JFAFA [DX3010]
R5F101JFDFA [DX3010]
R5F101JGAFA [DX3010]
R5F101JGDFA [DX3010]
R5F101JHAFA [DX3010]
R5F101JHDFA [DX3010]
R5F101JJAFA [DX3010]
R5F101JJDFA [DX3010]
R5F101JKAFA [DX3010]
R5F101JKDFA [DX3010]
R5F101JLAFA [DX3010]
R5F101JLDFA [DX3010]
R5F101LCABG [DX0001]
R5F101LCAFA [DX3012]
R5F101LCAFB [DX3011]
R5F101LCAFC [DX3085]
R5F101LCDBG [DX0001]
R5F101LCDFA [DX3012]
R5F101LCDFB [DX3011]
R5F101LCDFC [DX3085]
R5F101LDABG [DX0001]
R5F101LDAFA [DX3012]
R5F101LDAFB [DX3011]
R5F101LDAFC [DX3085]
R5F101LDDBG [DX0001]
R5F101LDDFA [DX3012]
R5F101LDDFB [DX3011]
R5F101LDDFC [DX3085]

R5F101LEABG [DX0001]
R5F101LEAFB [DX3011]
R5F101LEDBG [DX0001]
R5F101LEDFB [DX3011]
R5F101LFABG [DX0001]
R5F101LFAFB [DX3011]
R5F101LFDBG [DX0001]
R5F101LFDFB [DX3011]
R5F101LGABG [DX0001]
R5F101LGAFB [DX3011]
R5F101LGDBG [DX0001]
R5F101LGDFB [DX3011]
R5F101LHABG [DX0001]
R5F101LHAFB [DX3011]
R5F101LHDBG [DX0001]
R5F101LHDFB [DX3011]
R5F101LJABG [DX0001]
R5F101LJAFB [DX3011]
R5F101LJDBG [DX0001]
R5F101LJDFB [DX3011]
R5F101LKABG [DX0001]
R5F101LKAFB [DX3011]
R5F101LKDBG [DX0001]
R5F101LKDFB [DX3011]
R5F101LLABG [DX0001]
R5F101LLAFB [DX3011]
R5F101LLDBG [DX0001]
R5F101LLDFB [DX3011]
R5F101MCAFA [DX3017]
R5F101MCDFA [DX3017]
R5F101MDAFA [DX3017]
R5F101MDDFA [DX3017]
R5F101MEAFA [DX3017]
R5F101MEDFA [DX3017]
R5F101MFAFA [DX3017]
R5F101MFDFA [DX3017]
R5F101MGAFA [DX3017]
R5F101MGDFA [DX3017]
R5F101MHAFA [DX3017]
R5F101MHDFA [DX3017]
R5F101MJAFA [DX3017]
R5F101MJDFA [DX3017]
R5F101MKAFA [DX3017]
R5F101MKDFA [DX3017]
R5F101MLAFA [DX3017]
R5F101MLDFA [DX3017]
R5F101PCAFA [DX3062]
R5F101PCDFA [DX3062]
R5F101LEAFA [DX3012]
R5F101LEAFC [DX3085]
R5F101LEDFA [DX3012]
R5F101LEDFC [DX3085]
R5F101LFAFA [DX3012]
R5F101LFAFC [DX3085]
R5F101LFDFA [DX3012]
R5F101LFDFC [DX3085]
R5F101LGAFA [DX3012]
R5F101LGAFC [DX3085]
R5F101LGDFA [DX3012]
R5F101LGDFC [DX3085]
R5F101LHAFA [DX3012]
R5F101LHAFC [DX3085]
R5F101LHDFA [DX3012]
R5F101LHDFC [DX3085]
R5F101LJAFA [DX3012]
R5F101LJAFC [DX3085]
R5F101LJDFA [DX3012]
R5F101LJDFC [DX3085]
R5F101LKAFA [DX3012]
R5F101LKAFC [DX3085]
R5F101LKDFA [DX3012]
R5F101LKDFC [DX3085]
R5F101LLAFA [DX3012]
R5F101LLAFC [DX3085]
R5F101LLDFA [DX3012]
R5F101LLDFC [DX3085]
R5F101MCAFB [DX3016]
R5F101MCDFB [DX3016]
R5F101MDAFB [DX3016]
R5F101MDDFB [DX3016]
R5F101MEAFB [DX3016]
R5F101MEDFB [DX3016]
R5F101MFAFB [DX3016]
R5F101MFDFB [DX3016]
R5F101MGAFB [DX3016]
R5F101MGDFB [DX3016]
R5F101MHAFB [DX3016]
R5F101MHDFB [DX3016]
R5F101MJAFB [DX3016]
R5F101MJDFB [DX3016]
R5F101MKAFB [DX3016]
R5F101MKDFB [DX3016]
R5F101MLAFB [DX3016]
R5F101MLDFB [DX3016]
R5F101PCAFB [DX3021]
R5F101PCDFB [DX3021]

R5F101PDAFA [DX3062]	R5F101PDAFB [DX3021]
R5F101PDDFA [DX3062]	R5F101PDDFB [DX3021]
R5F101PEAFA [DX3062]	R5F101PEAFB [DX3021]
R5F101PEDFA [DX3062]	R5F101PEDFB [DX3021]
R5F101PFAFA [DX3062]	R5F101PFAFB [DX3021]
R5F101PFDFA [DX3062]	R5F101PFDFB [DX3021]
R5F101PGAFA [DX3062]	R5F101PGAFB [DX3021]
R5F101PGDFA [DX3062]	R5F101PGDFB [DX3021]
R5F101PHAFA [DX3062]	R5F101PHAFB [DX3021]
R5F101PHDFA [DX3062]	R5F101PHDFB [DX3021]
R5F101PJAFA [DX3062]	R5F101PJAFB [DX3021]
R5F101PJDFA [DX3062]	R5F101PJDFB [DX3021]
R5F101PKAFA [DX3062]	R5F101PKAFB [DX3021]
R5F101PKDFA [DX3062]	R5F101PKDFB [DX3021]
R5F101PLAFA [DX3062]	R5F101PLAFB [DX3021]
R5F101PLDFA [DX3062]	R5F101PLDFB [DX3021]
R5F101SCAFB [DX3031]	R5F101SCDFB [DX3031]
R5F101SDAFB [DX3031]	R5F101SDDFB [DX3031]
R5F101SEAFB [DX3031]	R5F101SEDFB [DX3031]
R5F101SFAFB [DX3031]	R5F101SFDFB [DX3031]
R5F101SGAFB [DX3031]	R5F101SGDFB [DX3031]
R5F101SHAFB [DX3031]	R5F101SHDFB [DX3031]
R5F101SJAFB [DX3031]	R5F101SJDFB [DX3031]
R5F101SKAFB [DX3031]	R5F101SKDFB [DX3031]
R5F101SLAFB [DX3031]	R5F101SLDFB [DX3031]
R5F10266ASP [DX1067]	R5F10266DSP [DX1067]
R5F10267ASP [DX1067]	R5F10267DSP [DX1067]
R5F10268ASP [DX1067]	R5F10268DSP [DX1067]
R5F10269ASP [DX1067]	R5F10269DSP [DX1067]
R5F1026AASP [DX1067]	R5F1026ADSP [DX1067]
R5F10276ANA [DX4012]	R5F10276DNA [DX4012]
R5F10277ANA [DX4012]	R5F10277DNA [DX4012]
R5F10278ANA [DX4012]	R5F10278DNA [DX4012]
R5F10279ANA [DX4012]	R5F10279DNA [DX4012]
R5F1027AANA [DX4012]	R5F1027ADNA [DX4012]
R5F102A6ASP [DX1027]	R5F102A6DSP [DX1027]
R5F102A7ASP [DX1027]	R5F102A7DSP [DX1027]
R5F102A8ASP [DX1027]	R5F102A8DSP [DX1027]
R5F102A9ASP [DX1027]	R5F102A9DSP [DX1027]
R5F102AAASP [DX1027]	R5F102AADSP [DX1027]
R5F10366ASP [DX1067]	R5F10366DSP [DX1067]
R5F10367ASP [DX1067]	R5F10367DSP [DX1067]
R5F10368ASP [DX1067]	R5F10368DSP [DX1067]
R5F10369ASP [DX1067]	R5F10369DSP [DX1067]
R5F1036AASP [DX1067]	R5F1036ADSP [DX1067]
R5F10376ANA [DX4012]	R5F10376DNA [DX4012]
R5F10377ANA [DX4012]	R5F10377DNA [DX4012]
R5F10378ANA [DX4012]	R5F10378DNA [DX4012]

R5F10379ANA [DX4012]	R5F10379DNA [DX4012]
R5F1037AANA [DX4012]	R5F1037ADNA [DX4012]
R5F103A6ASP [DX1027]	R5F103A6DSP [DX1027]
R5F103A7ASP [DX1027]	R5F103A7DSP [DX1027]
R5F103A8ASP [DX1027]	R5F103A8DSP [DX1027]
R5F103A9ASP [DX1027]	R5F103A9DSP [DX1027]
R5F103AAASP [DX1027]	R5F103AADSP [DX1027]
R5F104AAASP [DX1026]	R5F104AADSP [DX1026]
R5F104ACASP [DX1026]	R5F104ACDSP [DX1026]
R5F104ADASP [DX1026]	R5F104ADDSP [DX1026]
R5F104AEASP [DX1026]	R5F104AEDSP [DX1026]
R5F104AFASP [DX1026]	R5F104AFDSP [DX1026]
R5F104AGASP [DX1026]	R5F104AGDSP [DX1026]
R5F104AHASP [DX1026]	R5F104AHDSP [DX1026]
R5F104AJASP [DX1026]	R5F104AJDSP [DX1026]
R5F104AKASP [DX1026]	R5F104AKDSP [DX1026]
R5F104ALASP [DX1026]	R5F104ALDSP [DX1026]
R5F104BAAFP [DX3001]	R5F104BAANA [DX4015]
R5F104BADFP [DX3001]	R5F104BADNA [DX4015]
R5F104BCAFP [DX3001]	R5F104BCANA [DX4015]
R5F104BCDFP [DX3001]	R5F104BCDNA [DX4015]
R5F104BDAFP [DX3001]	R5F104BDANA [DX4015]
R5F104BDDFP [DX3001]	R5F104BDDNA [DX4015]
R5F104BEAFP [DX3001]	R5F104BEANA [DX4015]
R5F104BEDFP [DX3001]	R5F104BEDNA [DX4015]
R5F104BFAFP [DX3001]	R5F104BFANA [DX4015]
R5F104BFDFP [DX3001]	R5F104BFDNA [DX4015]
R5F104BGAFP [DX3001]	R5F104BGANA [DX4015]
R5F104BGDFP [DX3001]	R5F104BGDNA [DX4015]
R5F104BHAFP [DX3001]	R5F104BHANA [DX4015]
R5F104BHDFP [DX3001]	R5F104BHDNA [DX4015]
R5F104BJAFP [DX3001]	R5F104BJANA [DX4015]
R5F104BJDFP [DX3001]	R5F104BJDNA [DX4015]
R5F104BKAFP [DX3001]	R5F104BKANA [DX4015]
R5F104BKDFP [DX3001]	R5F104BKDNA [DX4015]
R5F104BLAFP [DX3001]	R5F104BLANA [DX4015]
R5F104BLDFP [DX3001]	R5F104BLDNA [DX4015]
R5F104CAALA [DX0001]	R5F104CADLA [DX0001]
R5F104CCALA [DX0001]	R5F104CCDLA [DX0001]
R5F104CDALA [DX0001]	R5F104CDDLA [DX0001]
R5F104CEALA [DX0001]	R5F104CEDLA [DX0001]
R5F104CFALA [DX0001]	R5F104CFDLA [DX0001]
R5F104CGALA [DX0001]	R5F104CGDLA [DX0001]
R5F104CHALA [DX0001]	R5F104CHDLA [DX0001]
R5F104CJALA [DX0001]	R5F104CJDLA [DX0001]
R5F104CKALA [DX0001]	R5F104CKDLA [DX0001]
R5F104CLALA [DX0001]	R5F104CLDLA [DX0001]
R5F104EAANA [DX4017]	R5F104EADNA [DX4017]

R5F104ECANA [DX4017]	R5F104ECDNA [DX4017]
R5F104EDANA [DX4017]	R5F104EDDNA [DX4017]
R5F104EEANA [DX4017]	R5F104EEDNA [DX4017]
R5F104EFANA [DX4017]	R5F104EFDNA [DX4017]
R5F104EGANA [DX4017]	R5F104EGDNA [DX4017]
R5F104EHANA [DX4017]	R5F104EHDNA [DX4017]
R5F104EJANA [DX4017]	R5F104EJDNA [DX4017]
R5F104EKANA [DX4017]	R5F104EKDNA [DX4017]
R5F104ELANA [DX4017]	R5F104ELDNA [DX4017]
R5F104FAAFP [DX3002]	R5F104FADFP [DX3002]
R5F104FCAFP [DX3002]	R5F104FCDFP [DX3002]
R5F104FDAFP [DX3002]	R5F104FDDFP [DX3002]
R5F104FEAFP [DX3002]	R5F104FEDFP [DX3002]
R5F104FFAFP [DX3002]	R5F104FFDFP [DX3002]
R5F104FGAFP [DX3002]	R5F104FGDFP [DX3002]
R5F104FHAFP [DX3002]	R5F104FHDFP [DX3002]
R5F104FJAFP [DX3002]	R5F104FJDFP [DX3002]
R5F104FKAFP [DX3002]	R5F104FKDFP [DX3002]
R5F104FLAFP [DX3002]	R5F104FLDFP [DX3002]
R5F104GAAFB [DX3007]	R5F104GAANA [DX4021]
R5F104GADFB [DX3007]	R5F104GADNA [DX4021]
R5F104GCAFB [DX3007]	R5F104GCANA [DX4021]
R5F104GCDFB [DX3007]	R5F104GCDNA [DX4021]
R5F104GDAFB [DX3007]	R5F104GDANA [DX4021]
R5F104GDDFB [DX3007]	R5F104GDDNA [DX4021]
R5F104GEAFB [DX3007]	R5F104GEANA [DX4021]
R5F104GEDFB [DX3007]	R5F104GEDNA [DX4021]
R5F104GFAFB [DX3007]	R5F104GFANA [DX4021]
R5F104GFDFB [DX3007]	R5F104GFDNA [DX4021]
R5F104GGAFB [DX3007]	R5F104GGANA [DX4021]
R5F104GGDFB [DX3007]	R5F104GGDNA [DX4021]
R5F104GHAFB [DX3007]	R5F104GHANA [DX4021]
R5F104GHDFB [DX3007]	R5F104GHDNA [DX4021]
R5F104GJAFB [DX3007]	R5F104GJANA [DX4021]
R5F104GJDFB [DX3007]	R5F104GJDNA [DX4021]
R5F104GKAFB [DX3007]	R5F104GKANA [DX4021]
R5F104GKDFB [DX3007]	R5F104GKDNA [DX4021]
R5F104GLAFB [DX3007]	R5F104GLANA [DX4021]
R5F104GLDFB [DX3007]	R5F104GLDNA [DX4021]
R5F104JCAFA [DX3010]	R5F104JCDFA [DX3010]
R5F104JDAFA [DX3010]	R5F104JDDFA [DX3010]
R5F104JEAFA [DX3010]	R5F104JEDFA [DX3010]
R5F104JFAFA [DX3010]	R5F104JFDFA [DX3010]
R5F104JGAFA [DX3010]	R5F104JGDFA [DX3010]
R5F104JHAFA [DX3010]	R5F104JHDFA [DX3010]
R5F104JJAFA [DX3010]	R5F104JJDFA [DX3010]
R5F104JKAFA [DX3010]	R5F104JKDFA [DX3010]
R5F104JLAFA [DX3010]	R5F104JLDFA [DX3010]

R5F104LCAFA [DX3012]
R5F104LCAFB [DX3011]
R5F104LCAFP [DX3013]
R5F104LCALA [DX0001]
R5F104LCDFA [DX3012]
R5F104LCDFB [DX3011]
R5F104LCDFP [DX3013]
R5F104LCDLA [DX0001]
R5F104LDAFA [DX3012]
R5F104LDAFB [DX3011]
R5F104LDAFP [DX3013]
R5F104LDALA [DX0001]
R5F104LDDFA [DX3012]
R5F104LDDFB [DX3011]
R5F104LDDFP [DX3013]
R5F104LDDLA [DX0001]
R5F104LEAFA [DX3012]
R5F104LEAFB [DX3011]
R5F104LEAFP [DX3013]
R5F104LEALA [DX0001]
R5F104LEDFA [DX3012]
R5F104LEDFB [DX3011]
R5F104LEDFP [DX3013]
R5F104LEDLA [DX0001]
R5F104LFAFA [DX3012]
R5F104LFAFB [DX3011]
R5F104LFAFP [DX3013]
R5F104LFALA [DX0001]
R5F104LFDFA [DX3012]
R5F104LFDFB [DX3011]
R5F104LFDFP [DX3013]
R5F104LFDLA [DX0001]
R5F104LGAFA [DX3012]
R5F104LGAFB [DX3011]
R5F104LGAFP [DX3013]
R5F104LGALA [DX0001]
R5F104LGDFA [DX3012]
R5F104LGDFB [DX3011]
R5F104LGDFP [DX3013]
R5F104LGDLA [DX0001]
R5F104LHAFA [DX3012]
R5F104LHAFB [DX3011]
R5F104LHAFP [DX3013]
R5F104LHALA [DX0001]
R5F104LHDFA [DX3012]
R5F104LHDFB [DX3011]
R5F104LHDFP [DX3013]
R5F104LHDLA [DX0001]
R5F104LJAFA [DX3012]
R5F104LJAFB [DX3011]
R5F104LJAFP [DX3013]
R5F104LJALA [DX0001]
R5F104LJDFA [DX3012]
R5F104LJDFB [DX3011]
R5F104LJDFP [DX3013]
R5F104LJDLA [DX0001]
R5F104LKAFA [DX3012]
R5F104LKAFB [DX3011]
R5F104LKAFP [DX3013]
R5F104LKALA [DX0001]
R5F104LKDFA [DX3012]
R5F104LKDFB [DX3011]
R5F104LKDFP [DX3013]
R5F104LKDLA [DX0001]
R5F104LLAFA [DX3012]
R5F104LLAFB [DX3011]
R5F104LLAFP [DX3013]
R5F104LLALA [DX0001]
R5F104LLDFA [DX3012]
R5F104LLDFB [DX3011]
R5F104LLDFP [DX3013]
R5F104LLDLA [DX0001]
R5F104MCAFA [DX3017]
R5F104MCAFB [DX3016]
R5F104MCDFA [DX3017]
R5F104MCDFB [DX3016]
R5F104MDAFA [DX3017]
R5F104MDAFB [DX3016]
R5F104MDDFA [DX3017]
R5F104MDDFB [DX3016]
R5F104MEAFA [DX3017]
R5F104MEAFB [DX3016]
R5F104MEDFA [DX3017]
R5F104MEDFB [DX3016]
R5F104MFAFA [DX3017]
R5F104MFAFB [DX3016]
R5F104MFDFA [DX3017]
R5F104MFDFB [DX3016]
R5F104MGAFA [DX3017]
R5F104MGAFB [DX3016]
R5F104MGDFA [DX3017]
R5F104MGDFB [DX3016]
R5F104MHAFA [DX3017]
R5F104MHAFB [DX3016]
R5F104MHDFA [DX3017]
R5F104MHDFB [DX3016]

R5F104MJAFA [DX3017]
R5F104MJDFA [DX3017]
R5F104MKAFA [DX3017]
R5F104MKDFA [DX3017]
R5F104MLAFA [DX3017]
R5F104MLDFA [DX3017]
R5F104PCAFA [DX3023]
R5F104PCDFA [DX3023]
R5F104PDAFA [DX3023]
R5F104PDDFA [DX3023]
R5F104PEAFA [DX3023]
R5F104PEDFA [DX3023]
R5F104PFAFA [DX3023]
R5F104PFDFA [DX3023]
R5F104PGAFA [DX3023]
R5F104PGDFA [DX3023]
R5F104PHAFA [DX3023]
R5F104PHDFA [DX3023]
R5F104PJAFA [DX3023]
R5F104PJDFA [DX3023]
R5F104PKAFA [DX3023]
R5F104PKDFA [DX3023]
R5F104PLAFA [DX3023]
R5F104PLDFA [DX3023]
R5F104SCAFB [DX3031]
R5F104SDAFB [DX3031]
R5F104SEAFB [DX3031]
R5F104SFAFB [DX3031]
R5F104SGAFB [DX3031]
R5F104SHAFB [DX3031]
R5F104SJAFB [DX3031]
R5F104SKAFB [DX3031]
R5F104SLAFB [DX3031]
R5F1076CGSP [DX1001]
R5F107ACGSP [DX1087]
R5F107DCGSP [DX1027]
R5F10968JSP [DX1026]
R5F1096BJSP [DX1026]
R5F1096DJSP [DX1026]
R5F1096FJSP [DX1026]
R5F1096HJSP [DX1026]
R5F1096KJSP [DX1026]
R5F109A8JSP [DX1087]
R5F109ABJSP [DX1087]
R5F109ADJSP [DX1087]
R5F109AFJSP [DX1087]
R5F109AHJSP [DX1087]
R5F109AKJSP [DX1087]
R5F104MJAFB [DX3016]
R5F104MJDFB [DX3016]
R5F104MKAFB [DX3016]
R5F104MKDFB [DX3016]
R5F104MLAFB [DX3016]
R5F104MLDFB [DX3016]
R5F104PCAFB [DX3021]
R5F104PCDFB [DX3021]
R5F104PDAFB [DX3021]
R5F104PDDFB [DX3021]
R5F104PEAFB [DX3021]
R5F104PEDFB [DX3021]
R5F104PFAFB [DX3021]
R5F104PFDFB [DX3021]
R5F104PGAFB [DX3021]
R5F104PGDFB [DX3021]
R5F104PHAFB [DX3021]
R5F104PHDFB [DX3021]
R5F104PJAFB [DX3021]
R5F104PJDFB [DX3021]
R5F104PKAFB [DX3021]
R5F104PKDFB [DX3021]
R5F104PLAFB [DX3021]
R5F104PLDFB [DX3021]
R5F104SCDFB [DX3031]
R5F104SDDFB [DX3031]
R5F104SEDFB [DX3031]
R5F104SFDFB [DX3031]
R5F104SGDFB [DX3031]
R5F104SHDFB [DX3031]
R5F104SJDFB [DX3031]
R5F104SKDFB [DX3031]
R5F104SLDFB [DX3031]
R5F1076EGSP [DX1001]
R5F107AEGSP [DX1087]
R5F107DEGSP [DX1027]
R5F1096AJSP [DX1026]
R5F1096CJSP [DX1026]
R5F1096EJSP [DX1026]
R5F1096GJSP [DX1026]
R5F1096JJSP [DX1026]
R5F1096LJSP [DX1026]
R5F109AAJSP [DX1087]
R5F109ACJSP [DX1087]
R5F109AEJSP [DX1087]
R5F109AGJSP [DX1087]
R5F109AJJSP [DX1087]
R5F109ALJSP [DX1087]

R5F109B8JFP [DX3001]
R5F109BAJFP [DX3001]
R5F109BBJFP [DX3001]
R5F109BCJFP [DX3001]
R5F109BDJFP [DX3001]
R5F109BEJFP [DX3001]
R5F109BFJFP [DX3001]
R5F109BGJFP [DX3001]
R5F109BHJFP [DX3001]
R5F109BJJFP [DX3001]
R5F109BKJFP [DX3001]
R5F109BLJFP [DX3001]
R5F109C8JLA [DX0001]
R5F109CBJLA [DX0001]
R5F109CDJLA [DX0001]
R5F109CFJLA [DX0001]
R5F109CHJLA [DX0001]
R5F109CKJLA [DX0001]
R5F109E8JNA [DX4017]
R5F109EBJNA [DX4017]
R5F109EDJNA [DX4017]
R5F109EFJNA [DX4017]
R5F109EHJNA [DX4017]
R5F109EKJNA [DX4017]
R5F109F8JFP [DX3002]
R5F109FBJFP [DX3002]
R5F109FDJFP [DX3002]
R5F109FFJFP [DX3002]
R5F109FHJFP [DX3002]
R5F109FKJFP [DX3002]
R5F109G8JFB [DX3007]
R5F109GAJFB [DX3007]
R5F109GBJFB [DX3007]
R5F109GCJFB [DX3007]
R5F109GDJFB [DX3007]
R5F109GEJFB [DX3007]
R5F109GFJFB [DX3007]
R5F109GGJFB [DX3007]
R5F109GHJFB [DX3007]
R5F109GJJFB [DX3007]
R5F109GKJFB [DX3007]
R5F109GLJFB [DX3007]
R5F109L8JFB [DX3011]
R5F109LBJFB [DX3011]
R5F109LDJFB [DX3011]
R5F109LFJFB [DX3011]
R5F109LHJFB [DX3011]
R5F109LKJFB [DX3011]
R5F109B8JNA [DX4015]
R5F109BAJNA [DX4015]
R5F109BBJNA [DX4015]
R5F109BCJNA [DX4015]
R5F109BDJNA [DX4015]
R5F109BEJNA [DX4015]
R5F109BFJNA [DX4015]
R5F109BGJNA [DX4015]
R5F109BHJNA [DX4015]
R5F109BJJNA [DX4015]
R5F109BKJNA [DX4015]
R5F109BLJNA [DX4015]
R5F109CAJLA [DX0001]
R5F109CCJLA [DX0001]
R5F109CEJLA [DX0001]
R5F109CGJLA [DX0001]
R5F109CJJLA [DX0001]
R5F109CLJLA [DX0001]
R5F109EAJNA [DX4017]
R5F109ECJNA [DX4017]
R5F109EEJNA [DX4017]
R5F109EGJNA [DX4017]
R5F109EJJNA [DX4017]
R5F109ELJNA [DX4017]
R5F109FAJFP [DX3002]
R5F109FCJFP [DX3002]
R5F109FEJFP [DX3002]
R5F109FGJFP [DX3002]
R5F109FJJFP [DX3002]
R5F109FLJFP [DX3002]
R5F109G8JNA [DX4021]
R5F109GAJNA [DX4021]
R5F109GBJNA [DX4021]
R5F109GCJNA [DX4021]
R5F109GDJNA [DX4021]
R5F109GEJNA [DX4021]
R5F109GFJNA [DX4021]
R5F109GGJNA [DX4021]
R5F109GHJNA [DX4021]
R5F109GJJNA [DX4021]
R5F109GKJNA [DX4021]
R5F109GLJNA [DX4021]
R5F109LAJFB [DX3011]
R5F109LCJFB [DX3011]
R5F109LEJFB [DX3011]
R5F109LGJFB [DX3011]
R5F109LJJFB [DX3011]
R5F109LLJFB [DX3011]

R5F10A68KSP [DX1026]
R5F10A68LSP [DX1026]
R5F10A68YSP [DX1026]
R5F10A6AKSP [DX1026]
R5F10A6ALSP [DX1026]
R5F10A6AYSP [DX1026]
R5F10A6BKSP [DX1026]
R5F10A6BLSP [DX1026]
R5F10A6BYSP [DX1026]
R5F10A6CKSP [DX1026]
R5F10A6CLSP [DX1026]
R5F10A6CYSP [DX1026]
R5F10A6DKSP [DX1026]
R5F10A6DLSP [DX1026]
R5F10A6DYSP [DX1026]
R5F10A6EKSP [DX1026]
R5F10A6ELSP [DX1026]
R5F10A6EYSP [DX1026]
R5F10A6FKSP [DX1026]
R5F10A6FLSP [DX1026]
R5F10A6FYSP [DX1026]
R5F10A6GKSP [DX1026]
R5F10A6GLSP [DX1026]
R5F10A6GYSP [DX1026]
R5F10A6HKSP [DX1026]
R5F10A6HLSP [DX1026]
R5F10A6HYSP [DX1026]
R5F10A6KKSP [DX1026]
R5F10A6KLSP [DX1026]
R5F10A6KYSP [DX1026]
R5F10A6LKSP [DX1026]
R5F10A6LLSP [DX1026]
R5F10A6LYSP [DX1026]
R5F10A6YYSP [DX1026]
R5F10AA8KSP [DX1087]
R5F10AA8LSP [DX1087]
R5F10AA8YSP [DX1087]
R5F10AAAKSP [DX1087]
R5F10AAALSP [DX1087]
R5F10AAAYSP [DX1087]
R5F10AABKSP [DX1087]
R5F10AABLSP [DX1087]
R5F10AABYSP [DX1087]
R5F10AACKSP [DX1087]
R5F10AACLSP [DX1087]
R5F10AACYSP [DX1087]
R5F10AADKSP [DX1087]
R5F10AADLSP [DX1087]
R5F10AADYSP [DX1087]
R5F10AAEKSP [DX1087]
R5F10AAELSP [DX1087]
R5F10AAEYSP [DX1087]
R5F10AAFKSP [DX1087]
R5F10AAFLSP [DX1087]
R5F10AAFYSP [DX1087]
R5F10AAGKSP [DX1087]
R5F10AAGLSP [DX1087]
R5F10AAGYSP [DX1087]
R5F10AAHKSP [DX1087]
R5F10AAHLSP [DX1087]
R5F10AAHYSP [DX1087]
R5F10AAKKSP [DX1087]
R5F10AAKLSP [DX1087]
R5F10AAKYSP [DX1087]
R5F10AALKSP [DX1087]
R5F10AALLSP [DX1087]
R5F10AALYSP [DX1087]
R5F10AAYYSP [DX1087]
R5F10AB8KFP [DX3001]
R5F10AB8KNA [DX4015]
R5F10AB8LFP [DX3001]
R5F10AB8LNA [DX4015]
R5F10AB8YFP [DX3001]
R5F10AB8YNA [DX4015]
R5F10ABAKFP [DX3001]
R5F10ABAKNA [DX4015]
R5F10ABALFP [DX3001]
R5F10ABALNA [DX4015]
R5F10ABAYFP [DX3001]
R5F10ABAYNA [DX4015]
R5F10ABBKFP [DX3001]
R5F10ABBKNA [DX4015]
R5F10ABBLFP [DX3001]
R5F10ABBLNA [DX4015]
R5F10ABBYFP [DX3001]
R5F10ABBYNA [DX4015]
R5F10ABCKFP [DX3001]
R5F10ABCKNA [DX4015]
R5F10ABCLFP [DX3001]
R5F10ABCLNA [DX4015]
R5F10ABCYFP [DX3001]
R5F10ABCYNA [DX4015]
R5F10ABDKFP [DX3001]
R5F10ABDKNA [DX4015]
R5F10ABDLFP [DX3001]
R5F10ABDLNA [DX4015]

R5F10ABDYFP [DX3001]
R5F10ABEKFP [DX3001]
R5F10ABELFP [DX3001]
R5F10ABEYFP [DX3001]
R5F10ABFKFP [DX3001]
R5F10ABFLFP [DX3001]
R5F10ABFYFP [DX3001]
R5F10ABGKFP [DX3001]
R5F10ABGLFP [DX3001]
R5F10ABGYFP [DX3001]
R5F10ABHKFP [DX3001]
R5F10ABHLFP [DX3001]
R5F10ABHYFP [DX3001]
R5F10ABKKFP [DX3001]
R5F10ABKLFP [DX3001]
R5F10ABKYFP [DX3001]
R5F10ABLKFP [DX3001]
R5F10ABLLFP [DX3001]
R5F10ABLYFP [DX3001]
R5F10ABYYFP [DX3001]
R5F10AC8KLA [DX0001]
R5F10AC8YLA [DX0001]
R5F10ACALLA [DX0001]
R5F10ACBKLA [DX0001]
R5F10ACBYLA [DX0001]
R5F10ACCLLA [DX0001]
R5F10ACDKLA [DX0001]
R5F10ACDYLA [DX0001]
R5F10ACELLA [DX0001]
R5F10ACFKLA [DX0001]
R5F10ACFYLA [DX0001]
R5F10ACGLLA [DX0001]
R5F10ACHKLA [DX0001]
R5F10ACHYLA [DX0001]
R5F10ACKLLA [DX0001]
R5F10ACLKLA [DX0001]
R5F10ACLYLA [DX0001]
R5F10AE8KNA [DX4017]
R5F10AE8YNA [DX4017]
R5F10AEALNA [DX4017]
R5F10AEBKNA [DX4017]
R5F10AEBYNA [DX4017]
R5F10AECLNA [DX4017]
R5F10AEDKNA [DX4017]
R5F10AEDYNA [DX4017]
R5F10AEELNA [DX4017]
R5F10AEFKNA [DX4017]
R5F10AEFYNA [DX4017]
R5F10ABDYNA [DX4015]
R5F10ABEKNA [DX4015]
R5F10ABELNA [DX4015]
R5F10ABEYNA [DX4015]
R5F10ABFKNA [DX4015]
R5F10ABFLNA [DX4015]
R5F10ABFYNA [DX4015]
R5F10ABGKNA [DX4015]
R5F10ABGLNA [DX4015]
R5F10ABGYNA [DX4015]
R5F10ABHKNA [DX4015]
R5F10ABHLNA [DX4015]
R5F10ABHYNA [DX4015]
R5F10ABKKNA [DX4015]
R5F10ABKLNA [DX4015]
R5F10ABKYNA [DX4015]
R5F10ABLKNA [DX4015]
R5F10ABLLNA [DX4015]
R5F10ABLYNA [DX4015]
R5F10ABYYNA [DX4015]
R5F10AC8LLA [DX0001]
R5F10ACAKLA [DX0001]
R5F10ACAYLA [DX0001]
R5F10ACBLLA [DX0001]
R5F10ACCKLA [DX0001]
R5F10ACCYLA [DX0001]
R5F10ACDLLA [DX0001]
R5F10ACEKLA [DX0001]
R5F10ACEYLA [DX0001]
R5F10ACFLLA [DX0001]
R5F10ACGKLA [DX0001]
R5F10ACGYLA [DX0001]
R5F10ACHLLA [DX0001]
R5F10ACKKLA [DX0001]
R5F10ACKYLA [DX0001]
R5F10ACLLLA [DX0001]
R5F10ACYYLA [DX0001]
R5F10AE8LNA [DX4017]
R5F10AEAKNA [DX4017]
R5F10AEAYNA [DX4017]
R5F10AEBLNA [DX4017]
R5F10AECKNA [DX4017]
R5F10AECYNA [DX4017]
R5F10AEDLNA [DX4017]
R5F10AEEKNA [DX4017]
R5F10AEEYNA [DX4017]
R5F10AEFLNA [DX4017]
R5F10AEGKNA [DX4017]

R5F10AEGLNA [DX4017]
R5F10AEGYNA [DX4017]
R5F10AEHKNA [DX4017]
R5F10AEHLNA [DX4017]
R5F10AEHYNA [DX4017]
R5F10AEKKNA [DX4017]
R5F10AEKLNA [DX4017]
R5F10AEKYNA [DX4017]
R5F10AELKNA [DX4017]
R5F10AELLNA [DX4017]
R5F10AELYNA [DX4017]
R5F10AEYYNA [DX4017]
R5F10AF8KFP [DX3002]
R5F10AF8LFP [DX3002]
R5F10AF8YFP [DX3002]
R5F10AFAKFP [DX3002]
R5F10AFALFP [DX3002]
R5F10AFAYFP [DX3002]
R5F10AFBKFP [DX3002]
R5F10AFBLFP [DX3002]
R5F10AFBYFP [DX3002]
R5F10AFCKFP [DX3002]
R5F10AFCLFP [DX3002]
R5F10AFCYFP [DX3002]
R5F10AFDKFP [DX3002]
R5F10AFDLFP [DX3002]
R5F10AFDYFP [DX3002]
R5F10AFEKFP [DX3002]
R5F10AFELFP [DX3002]
R5F10AFEYFP [DX3002]
R5F10AFFKFP [DX3002]
R5F10AFFLFP [DX3002]
R5F10AFFYFP [DX3002]
R5F10AFGKFP [DX3002]
R5F10AFGLFP [DX3002]
R5F10AFGYFP [DX3002]
R5F10AFHKFP [DX3002]
R5F10AFHLFP [DX3002]
R5F10AFHYFP [DX3002]
R5F10AFKKFP [DX3002]
R5F10AFKLFP [DX3002]
R5F10AFKYFP [DX3002]
R5F10AFLKFP [DX3002]
R5F10AFLLFP [DX3002]
R5F10AFLYFP [DX3002]
R5F10AFYYFP [DX3002]
R5F10AG8KFB [DX3007]
R5F10AG8KNA [DX4021]
R5F10AG8LFB [DX3007]
R5F10AG8LNA [DX4021]
R5F10AG8YFB [DX3007]
R5F10AG8YNA [DX4021]
R5F10AGAKFB [DX3007]
R5F10AGAKNA [DX4021]
R5F10AGALFB [DX3007]
R5F10AGALNA [DX4021]
R5F10AGAYFB [DX3007]
R5F10AGAYNA [DX4021]
R5F10AGBKFB [DX3007]
R5F10AGBKNA [DX4021]
R5F10AGBLFB [DX3007]
R5F10AGBLNA [DX4021]
R5F10AGBYFB [DX3007]
R5F10AGBYNA [DX4021]
R5F10AGCKFB [DX3007]
R5F10AGCKNA [DX4021]
R5F10AGCLFB [DX3007]
R5F10AGCLNA [DX4021]
R5F10AGCYFB [DX3007]
R5F10AGCYNA [DX4021]
R5F10AGDKFB [DX3007]
R5F10AGDKNA [DX4021]
R5F10AGDLFB [DX3007]
R5F10AGDLNA [DX4021]
R5F10AGDYFB [DX3007]
R5F10AGDYNA [DX4021]
R5F10AGEKFB [DX3007]
R5F10AGEKNA [DX4021]
R5F10AGELFB [DX3007]
R5F10AGELNA [DX4021]
R5F10AGEYFB [DX3007]
R5F10AGEYNA [DX4021]
R5F10AGFKFB [DX3007]
R5F10AGFKNA [DX4021]
R5F10AGFLFB [DX3007]
R5F10AGFLNA [DX4021]
R5F10AGFYFB [DX3007]
R5F10AGFYNA [DX4021]
R5F10AGGKFB [DX3007]
R5F10AGGKNA [DX4021]
R5F10AGGLFB [DX3007]
R5F10AGGLNA [DX4021]
R5F10AGGYFB [DX3007]
R5F10AGGYNA [DX4021]
R5F10AGHKFB [DX3007]
R5F10AGHKNA [DX4021]

R5F10AGHLFB [DX3007]
R5F10AGHYFB [DX3007]
R5F10AGKKFB [DX3007]
R5F10AGKLFB [DX3007]
R5F10AGKYFB [DX3007]
R5F10AGLKFB [DX3007]
R5F10AGLLFB [DX3007]
R5F10AGLYFB [DX3007]
R5F10AGYYFB [DX3007]
R5F10AL8KFB [DX3011]
R5F10AL8YFB [DX3011]
R5F10ALALFB [DX3011]
R5F10ALBKFB [DX3011]
R5F10ALBYFB [DX3011]
R5F10ALCLFB [DX3011]
R5F10ALDKFB [DX3011]
R5F10ALDYFB [DX3011]
R5F10ALELFB [DX3011]
R5F10ALFKFB [DX3011]
R5F10ALFYFB [DX3011]
R5F10ALGLFB [DX3011]
R5F10ALHKFB [DX3011]
R5F10ALHYFB [DX3011]
R5F10ALKLFB [DX3011]
R5F10ALLKFB [DX3011]
R5F10ALLYFB [DX3011]
R5F10B68KSP [DX1026]
R5F10B68YSP [DX1026]
R5F10B6ALSP [DX1026]
R5F10B6BKSP [DX1026]
R5F10B6BYSP [DX1026]
R5F10B6CLSP [DX1026]
R5F10B6DKSP [DX1026]
R5F10B6DYSP [DX1026]
R5F10B6ELSP [DX1026]
R5F10B6FKSP [DX1026]
R5F10B6FYSP [DX1026]
R5F10B6GLSP [DX1026]
R5F10B6HKSP [DX1026]
R5F10B6HYSP [DX1026]
R5F10B6KLSP [DX1026]
R5F10B6LKSP [DX1026]
R5F10B6LYSP [DX1026]
R5F10BA8KSP [DX1087]
R5F10BA8YSP [DX1087]
R5F10BAALSP [DX1087]
R5F10BABKSP [DX1087]
R5F10BABYSP [DX1087]
R5F10AGHLNA [DX4021]
R5F10AGHYNA [DX4021]
R5F10AGKKNA [DX4021]
R5F10AGKLNA [DX4021]
R5F10AGKYNA [DX4021]
R5F10AGLKNA [DX4021]
R5F10AGLLNA [DX4021]
R5F10AGLYNA [DX4021]
R5F10AGYYNA [DX4021]
R5F10AL8LFB [DX3011]
R5F10ALAKFB [DX3011]
R5F10ALAYFB [DX3011]
R5F10ALBLFB [DX3011]
R5F10ALCKFB [DX3011]
R5F10ALCYFB [DX3011]
R5F10ALDLFB [DX3011]
R5F10ALEKFB [DX3011]
R5F10ALEYFB [DX3011]
R5F10ALFLFB [DX3011]
R5F10ALGKFB [DX3011]
R5F10ALGYFB [DX3011]
R5F10ALHLFB [DX3011]
R5F10ALKKFB [DX3011]
R5F10ALKYFB [DX3011]
R5F10ALLLFB [DX3011]
R5F10ALYYFB [DX3011]
R5F10B68LSP [DX1026]
R5F10B6AKSP [DX1026]
R5F10B6AYSP [DX1026]
R5F10B6BLSP [DX1026]
R5F10B6CKSP [DX1026]
R5F10B6CYSP [DX1026]
R5F10B6DLSP [DX1026]
R5F10B6EKSP [DX1026]
R5F10B6EYSP [DX1026]
R5F10B6FLSP [DX1026]
R5F10B6GKSP [DX1026]
R5F10B6GYSP [DX1026]
R5F10B6HLSP [DX1026]
R5F10B6KKSP [DX1026]
R5F10B6KYSP [DX1026]
R5F10B6LLSP [DX1026]
R5F10B6YYSP [DX1026]
R5F10BA8LSP [DX1087]
R5F10BAAKSP [DX1087]
R5F10BAAYSP [DX1087]
R5F10BABLSP [DX1087]
R5F10BACKSP [DX1087]

R5F10BACLSP [DX1087]
R5F10BACYSP [DX1087]
R5F10BADKSP [DX1087]
R5F10BADLSP [DX1087]
R5F10BADYSP [DX1087]
R5F10BAEKSP [DX1087]
R5F10BAELSP [DX1087]
R5F10BAEYSP [DX1087]
R5F10BAFKSP [DX1087]
R5F10BAFLSP [DX1087]
R5F10BAFYSP [DX1087]
R5F10BAGKSP [DX1087]
R5F10BAGLSP [DX1087]
R5F10BAGYSP [DX1087]
R5F10BAHKSP [DX1087]
R5F10BAHLSP [DX1087]
R5F10BAHYSP [DX1087]
R5F10BAKKSP [DX1087]
R5F10BAKLSP [DX1087]
R5F10BAKYSP [DX1087]
R5F10BALKSP [DX1087]
R5F10BALLSP [DX1087]
R5F10BALYSP [DX1087]
R5F10BAYYSP [DX1087]
R5F10BB8KFP [DX3001]
R5F10BB8KNA [DX4015]
R5F10BB8LFP [DX3001]
R5F10BB8LNA [DX4015]
R5F10BB8YFP [DX3001]
R5F10BB8YNA [DX4015]
R5F10BBAKFP [DX3001]
R5F10BBAKNA [DX4015]
R5F10BBALFP [DX3001]
R5F10BBALNA [DX4015]
R5F10BBAYFP [DX3001]
R5F10BBAYNA [DX4015]
R5F10BBBKFP [DX3001]
R5F10BBBKNA [DX4015]
R5F10BBBLFP [DX3001]
R5F10BBBLNA [DX4015]
R5F10BBBYFP [DX3001]
R5F10BBBYNA [DX4015]
R5F10BBCKFP [DX3001]
R5F10BBCKNA [DX4015]
R5F10BBCLFP [DX3001]
R5F10BBCLNA [DX4015]
R5F10BBCYFP [DX3001]
R5F10BBCYNA [DX4015]
R5F10BBDKFP [DX3001]
R5F10BBDKNA [DX4015]
R5F10BBDLFP [DX3001]
R5F10BBDLNA [DX4015]
R5F10BBDYFP [DX3001]
R5F10BBDYNA [DX4015]
R5F10BBEKFP [DX3001]
R5F10BBEKNA [DX4015]
R5F10BBELFP [DX3001]
R5F10BBELNA [DX4015]
R5F10BBEYFP [DX3001]
R5F10BBEYNA [DX4015]
R5F10BBFKFP [DX3001]
R5F10BBFKNA [DX4015]
R5F10BBFLFP [DX3001]
R5F10BBFLNA [DX4015]
R5F10BBFYFP [DX3001]
R5F10BBFYNA [DX4015]
R5F10BBGKFP [DX3001]
R5F10BBGKNA [DX4015]
R5F10BBGLFP [DX3001]
R5F10BBGLNA [DX4015]
R5F10BBGYFP [DX3001]
R5F10BBGYNA [DX4015]
R5F10BBHKFP [DX3001]
R5F10BBHKNA [DX4015]
R5F10BBHLFP [DX3001]
R5F10BBHLNA [DX4015]
R5F10BBHYFP [DX3001]
R5F10BBHYNA [DX4015]
R5F10BBKKFP [DX3001]
R5F10BBKKNA [DX4015]
R5F10BBKLFP [DX3001]
R5F10BBKLNA [DX4015]
R5F10BBKYFP [DX3001]
R5F10BBKYNA [DX4015]
R5F10BBLKFP [DX3001]
R5F10BBLKNA [DX4015]
R5F10BBLLFP [DX3001]
R5F10BBLLNA [DX4015]
R5F10BBLYFP [DX3001]
R5F10BBLYNA [DX4015]
R5F10BBYYFP [DX3001]
R5F10BBYYNA [DX4015]
R5F10BC8KLA [DX0001]
R5F10BC8LLA [DX0001]
R5F10BC8YLA [DX0001]
R5F10BCAKLA [DX0001]

R5F10BCALLA [DX0001]
R5F10BCAYLA [DX0001]
R5F10BCBKLA [DX0001]
R5F10BCBLLA [DX0001]
R5F10BCBYLA [DX0001]
R5F10BCCKLA [DX0001]
R5F10BCCLLA [DX0001]
R5F10BCCYLA [DX0001]
R5F10BCDKLA [DX0001]
R5F10BCDLLA [DX0001]
R5F10BCDYLA [DX0001]
R5F10BCEKLA [DX0001]
R5F10BCELLA [DX0001]
R5F10BCEYLA [DX0001]
R5F10BCFKLA [DX0001]
R5F10BCFLLA [DX0001]
R5F10BCFYLA [DX0001]
R5F10BCGKLA [DX0001]
R5F10BCGLLA [DX0001]
R5F10BCGYLA [DX0001]
R5F10BCHKLA [DX0001]
R5F10BCHLLA [DX0001]
R5F10BCHYLA [DX0001]
R5F10BCKKLA [DX0001]
R5F10BCKLLA [DX0001]
R5F10BCKYLA [DX0001]
R5F10BCLKLA [DX0001]
R5F10BCLLLA [DX0001]
R5F10BCLYLA [DX0001]
R5F10BCYYLA [DX0001]
R5F10BE8KNA [DX4017]
R5F10BE8LNA [DX4017]
R5F10BE8YNA [DX4017]
R5F10BEAKNA [DX4017]
R5F10BEALNA [DX4017]
R5F10BEAYNA [DX4017]
R5F10BEBKNA [DX4017]
R5F10BEBLNA [DX4017]
R5F10BEBYNA [DX4017]
R5F10BECKNA [DX4017]
R5F10BECLNA [DX4017]
R5F10BECYNA [DX4017]
R5F10BEDKNA [DX4017]
R5F10BEDLNA [DX4017]
R5F10BEDYNA [DX4017]
R5F10BEEKNA [DX4017]
R5F10BEELNA [DX4017]
R5F10BEEYNA [DX4017]
R5F10BEFKNA [DX4017]
R5F10BEFLNA [DX4017]
R5F10BEFYNA [DX4017]
R5F10BEGKNA [DX4017]
R5F10BEGLNA [DX4017]
R5F10BEGYNA [DX4017]
R5F10BEHKNA [DX4017]
R5F10BEHLNA [DX4017]
R5F10BEHYNA [DX4017]
R5F10BEKKNA [DX4017]
R5F10BEKLNA [DX4017]
R5F10BEKYNA [DX4017]
R5F10BELKNA [DX4017]
R5F10BELLNA [DX4017]
R5F10BELYNA [DX4017]
R5F10BEYYNA [DX4017]
R5F10BF8KFP [DX3002]
R5F10BF8LFP [DX3002]
R5F10BF8YFP [DX3002]
R5F10BFAKFP [DX3002]
R5F10BFALFP [DX3002]
R5F10BFAYFP [DX3002]
R5F10BFBKFP [DX3002]
R5F10BFBLFP [DX3002]
R5F10BFBYFP [DX3002]
R5F10BFCKFP [DX3002]
R5F10BFCLFP [DX3002]
R5F10BFCYFP [DX3002]
R5F10BFDKFP [DX3002]
R5F10BFDLFP [DX3002]
R5F10BFDYFP [DX3002]
R5F10BFEKFP [DX3002]
R5F10BFELFP [DX3002]
R5F10BFEYFP [DX3002]
R5F10BFFKFP [DX3002]
R5F10BFFLFP [DX3002]
R5F10BFFYFP [DX3002]
R5F10BFGKFP [DX3002]
R5F10BFGLFP [DX3002]
R5F10BFGYFP [DX3002]
R5F10BFHKFP [DX3002]
R5F10BFHLFP [DX3002]
R5F10BFHYFP [DX3002]
R5F10BFKKFP [DX3002]
R5F10BFKLFP [DX3002]
R5F10BFKYFP [DX3002]
R5F10BFLKFP [DX3002]
R5F10BFLLFP [DX3002]

R5F10BFLYFP [DX3002]
R5F10BFYYFP [DX3002]
R5F10BG8KFB [DX3007]
R5F10BG8KNA [DX4021]
R5F10BG8LFB [DX3007]
R5F10BG8LNA [DX4021]
R5F10BG8YFB [DX3007]
R5F10BG8YNA [DX4021]
R5F10BGAKFB [DX3007]
R5F10BGAKNA [DX4021]
R5F10BGALFB [DX3007]
R5F10BGALNA [DX4021]
R5F10BGAYFB [DX3007]
R5F10BGAYNA [DX4021]
R5F10BGBKFB [DX3007]
R5F10BGBKNA [DX4021]
R5F10BGBLFB [DX3007]
R5F10BGBLNA [DX4021]
R5F10BGBYFB [DX3007]
R5F10BGBYNA [DX4021]
R5F10BGCKFB [DX3007]
R5F10BGCKNA [DX4021]
R5F10BGCLFB [DX3007]
R5F10BGCLNA [DX4021]
R5F10BGCYFB [DX3007]
R5F10BGCYNA [DX4021]
R5F10BGDKFB [DX3007]
R5F10BGDKNA [DX4021]
R5F10BGDLFB [DX3007]
R5F10BGDLNA [DX4021]
R5F10BGDYFB [DX3007]
R5F10BGDYNA [DX4021]
R5F10BGEKFB [DX3007]
R5F10BGEKNA [DX4021]
R5F10BGELFB [DX3007]
R5F10BGELNA [DX4021]
R5F10BGEYFB [DX3007]
R5F10BGEYNA [DX4021]
R5F10BGFKFB [DX3007]
R5F10BGFKNA [DX4021]
R5F10BGFLFB [DX3007]
R5F10BGFLNA [DX4021]
R5F10BGFYFB [DX3007]
R5F10BGFYNA [DX4021]
R5F10BGGKFB [DX3007]
R5F10BGGKNA [DX4021]
R5F10BGGLFB [DX3007]
R5F10BGGLNA [DX4021]
R5F10BGGYFB [DX3007]
R5F10BGGYNA [DX4021]
R5F10BGHKFB [DX3007]
R5F10BGHKNA [DX4021]
R5F10BGHLFB [DX3007]
R5F10BGHLNA [DX4021]
R5F10BGHYFB [DX3007]
R5F10BGHYNA [DX4021]
R5F10BGKKFB [DX3007]
R5F10BGKKNA [DX4021]
R5F10BGKLFB [DX3007]
R5F10BGKLNA [DX4021]
R5F10BGKYFB [DX3007]
R5F10BGKYNA [DX4021]
R5F10BGLKFB [DX3007]
R5F10BGLKNA [DX4021]
R5F10BGLLFB [DX3007]
R5F10BGLLNA [DX4021]
R5F10BGLYFB [DX3007]
R5F10BGLYNA [DX4021]
R5F10BGYYFB [DX3007]
R5F10BGYYNA [DX4021]
R5F10BL8KFB [DX3011]
R5F10BL8LFB [DX3011]
R5F10BL8YFB [DX3011]
R5F10BLAKFB [DX3011]
R5F10BLALFB [DX3011]
R5F10BLAYFB [DX3011]
R5F10BLBKFB [DX3011]
R5F10BLBLFB [DX3011]
R5F10BLBYFB [DX3011]
R5F10BLCKFB [DX3011]
R5F10BLCLFB [DX3011]
R5F10BLCYFB [DX3011]
R5F10BLDKFB [DX3011]
R5F10BLDLFB [DX3011]
R5F10BLDYFB [DX3011]
R5F10BLEKFB [DX3011]
R5F10BLELFB [DX3011]
R5F10BLEYFB [DX3011]
R5F10BLFKFB [DX3011]
R5F10BLFLFB [DX3011]
R5F10BLFYFB [DX3011]
R5F10BLGKFB [DX3011]
R5F10BLGLFB [DX3011]
R5F10BLGYFB [DX3011]
R5F10BLHKFB [DX3011]
R5F10BLHLFB [DX3011]

R5F10BLHYFB [DX3011]
R5F10BLKKFB [DX3011]
R5F10BLKLFB [DX3011]
R5F10BLKYFB [DX3011]
R5F10BLLKFB [DX3011]
R5F10BLLLFB [DX3011]
R5F10BLLYFB [DX3011]
R5F10BLYYFB [DX3011]
R5F10C6AJSP [DX1026]
R5F10C6ALSP [DX1026]
R5F10C6CJSP [DX1026]
R5F10C6CLSP [DX1026]
R5F10C6DJSP [DX1026]
R5F10C6DLSP [DX1026]
R5F10C6EJSP [DX1026]
R5F10C6ELSP [DX1026]
R5F10C6FJSP [DX1026]
R5F10C6FLSP [DX1026]
R5F10C6GJSP [DX1026]
R5F10C6GLSP [DX1026]
R5F10C6HJSP [DX1026]
R5F10C6HLSP [DX1026]
R5F10C6JJSP [DX1026]
R5F10C6JLSP [DX1026]
R5F10C6KJSP [DX1026]
R5F10C6KLSP [DX1026]
R5F10C6LJSP [DX1026]
R5F10C6LLSP [DX1026]
R5F10C7AJNA [DX4012]
R5F10C7ALNA [DX4012]
R5F10C7CJNA [DX4012]
R5F10C7CLNA [DX4012]
R5F10C7DJNA [DX4012]
R5F10C7DLNA [DX4012]
R5F10C7EJNA [DX4012]
R5F10C7ELNA [DX4012]
R5F10C7FJNA [DX4012]
R5F10C7FLNA [DX4012]
R5F10C7GJNA [DX4012]
R5F10C7GLNA [DX4012]
R5F10C7HJNA [DX4012]
R5F10C7HLNA [DX4012]
R5F10C7JJNA [DX4012]
R5F10C7JLNA [DX4012]
R5F10C7KJNA [DX4012]
R5F10C7KLNA [DX4012]
R5F10C7LJNA [DX4012]
R5F10C7LLNA [DX4012]
R5F10C8AJLA [DX0001]
R5F10C8ALLA [DX0001]
R5F10C8CJLA [DX0001]
R5F10C8CLLA [DX0001]
R5F10C8DJLA [DX0001]
R5F10C8DLLA [DX0001]
R5F10C8EJLA [DX0001]
R5F10C8ELLA [DX0001]
R5F10C8FJLA [DX0001]
R5F10C8FLLA [DX0001]
R5F10C8GJLA [DX0001]
R5F10C8GLLA [DX0001]
R5F10C8HJLA [DX0001]
R5F10C8HLLA [DX0001]
R5F10C8JJLA [DX0001]
R5F10C8JLLA [DX0001]
R5F10C8KJLA [DX0001]
R5F10C8KLLA [DX0001]
R5F10C8LJLA [DX0001]
R5F10C8LLLA [DX0001]
R5F10CAAJSP [DX1087]
R5F10CAALSP [DX1087]
R5F10CACJSP [DX1087]
R5F10CACLSP [DX1087]
R5F10CADJSP [DX1087]
R5F10CADLSP [DX1087]
R5F10CAEJSP [DX1087]
R5F10CAELSP [DX1087]
R5F10CAFJSP [DX1087]
R5F10CAFLSP [DX1087]
R5F10CAGJSP [DX1087]
R5F10CAGLSP [DX1087]
R5F10CAHJSP [DX1087]
R5F10CAHLSP [DX1087]
R5F10CAJJSP [DX1087]
R5F10CAJLSP [DX1087]
R5F10CAKJSP [DX1087]
R5F10CAKLSP [DX1087]
R5F10CALJSP [DX1087]
R5F10CALLSP [DX1087]
R5F10CBAJNA [DX4015]
R5F10CBALNA [DX4015]
R5F10CBCJNA [DX4015]
R5F10CBCLNA [DX4015]
R5F10CBDJNA [DX4015]
R5F10CBDLNA [DX4015]
R5F10CBEJNA [DX4015]
R5F10CBELNA [DX4015]

R5F10CBFJNA [DX4015]	R5F10CBFLNA [DX4015]
R5F10CBGJNA [DX4015]	R5F10CBGLNA [DX4015]
R5F10CBHJNA [DX4015]	R5F10CBHLNA [DX4015]
R5F10CBJJNA [DX4015]	R5F10CBJLNA [DX4015]
R5F10CBKJNA [DX4015]	R5F10CBKLNA [DX4015]
R5F10CBLJNA [DX4015]	R5F10CBLLNA [DX4015]
R5F10CCAJLA [DX0001]	R5F10CCALLA [DX0001]
R5F10CCCJLA [DX0001]	R5F10CCCLLA [DX0001]
R5F10CCDJLA [DX0001]	R5F10CCDLLA [DX0001]
R5F10CCEJLA [DX0001]	R5F10CCELLA [DX0001]
R5F10CCFJLA [DX0001]	R5F10CCFLLA [DX0001]
R5F10CCGJLA [DX0001]	R5F10CCGLLA [DX0001]
R5F10CCHJLA [DX0001]	R5F10CCHLLA [DX0001]
R5F10CCJJLA [DX0001]	R5F10CCJLLA [DX0001]
R5F10CCKJLA [DX0001]	R5F10CCKLLA [DX0001]
R5F10CCLJLA [DX0001]	R5F10CCLLLA [DX0001]
R5F10CEAJNA [DX4017]	R5F10CEALNA [DX4017]
R5F10CECJNA [DX4017]	R5F10CECLNA [DX4017]
R5F10CEDJNA [DX4017]	R5F10CEDLNA [DX4017]
R5F10CEEJNA [DX4017]	R5F10CEELNA [DX4017]
R5F10CEFJNA [DX4017]	R5F10CEFLNA [DX4017]
R5F10CEGJNA [DX4017]	R5F10CEGLNA [DX4017]
R5F10CEHJNA [DX4017]	R5F10CEHLNA [DX4017]
R5F10CEJJNA [DX4017]	R5F10CEJLNA [DX4017]
R5F10CEKJNA [DX4017]	R5F10CEKLNA [DX4017]
R5F10CELJNA [DX4017]	R5F10CELLNA [DX4017]
R5F10CFAJFP [DX3005]	R5F10CFALFP [DX3005]
R5F10CFCJFP [DX3005]	R5F10CFCLFP [DX3005]
R5F10CFDJFP [DX3005]	R5F10CFDLFP [DX3005]
R5F10CFEJFP [DX3005]	R5F10CFELFP [DX3005]
R5F10CFFJFP [DX3005]	R5F10CFFLFP [DX3005]
R5F10CFGJFP [DX3005]	R5F10CFGLFP [DX3005]
R5F10CFHJFP [DX3005]	R5F10CFHLFP [DX3005]
R5F10CFJJFP [DX3005]	R5F10CFJLFP [DX3005]
R5F10CFKJFP [DX3005]	R5F10CFKLFP [DX3005]
R5F10CFLJFP [DX3005]	R5F10CFLLFP [DX3005]
R5F10CGAJFB [DX3007]	R5F10CGAJNA [DX4021]
R5F10CGALFB [DX3007]	R5F10CGALNA [DX4021]
R5F10CGCJFB [DX3007]	R5F10CGCJNA [DX4021]
R5F10CGCLFB [DX3007]	R5F10CGCLNA [DX4021]
R5F10CGDJFB [DX3007]	R5F10CGDJNA [DX4021]
R5F10CGDLFB [DX3007]	R5F10CGDLNA [DX4021]
R5F10CGEJFB [DX3007]	R5F10CGEJNA [DX4021]
R5F10CGELFB [DX3007]	R5F10CGELNA [DX4021]
R5F10CGFJFB [DX3007]	R5F10CGFJNA [DX4021]
R5F10CGFLFB [DX3007]	R5F10CGFLNA [DX4021]
R5F10CGGJFB [DX3007]	R5F10CGGJNA [DX4021]
R5F10CGGLFB [DX3007]	R5F10CGGLNA [DX4021]

R5F10CGHJFB [DX3007]
R5F10CGHLFB [DX3007]
R5F10CGJJFB [DX3007]
R5F10CGJLFB [DX3007]
R5F10CGKJFB [DX3007]
R5F10CGKLFB [DX3007]
R5F10CGLJFB [DX3007]
R5F10CGLLFB [DX3007]
R5F10CJCJFA [DX3010]
R5F10CJDJFA [DX3010]
R5F10CJEJFA [DX3010]
R5F10CJFJFA [DX3010]
R5F10CJGJFA [DX3010]
R5F10CJHJFA [DX3010]
R5F10CJJJFA [DX3010]
R5F10CJKJFA [DX3010]
R5F10CJLJFA [DX3010]
R5F10CLCJBG [DX0001]
R5F10CLCJFB [DX3011]
R5F10CLCLBG [DX0001]
R5F10CLCLFB [DX3011]
R5F10CLDJBG [DX0001]
R5F10CLDJFB [DX3011]
R5F10CLDLBG [DX0001]
R5F10CLDLFB [DX3011]
R5F10CLEJBG [DX0001]
R5F10CLEJFB [DX3011]
R5F10CLELBG [DX0001]
R5F10CLELFB [DX3011]
R5F10CLFJBG [DX0001]
R5F10CLFJFB [DX3011]
R5F10CLFLBG [DX0001]
R5F10CLFLFB [DX3011]
R5F10CLGJBG [DX0001]
R5F10CLGJFB [DX3011]
R5F10CLGLBG [DX0001]
R5F10CLGLFB [DX3011]
R5F10CLHJBG [DX0001]
R5F10CLHJFB [DX3011]
R5F10CLHLBG [DX0001]
R5F10CLHLFB [DX3011]
R5F10CLJJBG [DX0001]
R5F10CLJJFB [DX3011]
R5F10CLJLBG [DX0001]
R5F10CLJLFB [DX3011]
R5F10CLKJBG [DX0001]
R5F10CLKJFB [DX3011]
R5F10CLKLBG [DX0001]
R5F10CGHJNA [DX4021]
R5F10CGHLNA [DX4021]
R5F10CGJJNA [DX4021]
R5F10CGJLNA [DX4021]
R5F10CGKJNA [DX4021]
R5F10CGKLNA [DX4021]
R5F10CGLJNA [DX4021]
R5F10CGLLNA [DX4021]
R5F10CJCLFA [DX3010]
R5F10CJDLFA [DX3010]
R5F10CJELFA [DX3010]
R5F10CJFLFA [DX3010]
R5F10CJGLFA [DX3010]
R5F10CJHLFA [DX3010]
R5F10CJJLFA [DX3010]
R5F10CJKLFA [DX3010]
R5F10CJLLFA [DX3010]
R5F10CLCJFA [DX3012]
R5F10CLCJFC [DX3085]
R5F10CLCLFA [DX3012]
R5F10CLCLFC [DX3085]
R5F10CLDJFA [DX3012]
R5F10CLDJFC [DX3085]
R5F10CLDLFA [DX3012]
R5F10CLDLFC [DX3085]
R5F10CLEJFA [DX3012]
R5F10CLEJFC [DX3085]
R5F10CLELFA [DX3012]
R5F10CLELFC [DX3085]
R5F10CLFJFA [DX3012]
R5F10CLFJFC [DX3085]
R5F10CLFLFA [DX3012]
R5F10CLFLFC [DX3085]
R5F10CLGJFA [DX3012]
R5F10CLGJFC [DX3085]
R5F10CLGLFA [DX3012]
R5F10CLGLFC [DX3085]
R5F10CLHJFA [DX3012]
R5F10CLHJFC [DX3085]
R5F10CLHLFA [DX3012]
R5F10CLHLFC [DX3085]
R5F10CLJJFA [DX3012]
R5F10CLJJFC [DX3085]
R5F10CLJLFA [DX3012]
R5F10CLJLFC [DX3085]
R5F10CLKJFA [DX3012]
R5F10CLKJFC [DX3085]
R5F10CLKLFA [DX3012]

R5F10CLKLFB [DX3011]
R5F10CLLJBG [DX0001]
R5F10CLLJFB [DX3011]
R5F10CLLLBG [DX0001]
R5F10CLLLFB [DX3011]
R5F10CMCJFA [DX3018]
R5F10CMCLFA [DX3017]
R5F10CMDJFA [DX3018]
R5F10CMDLFA [DX3017]
R5F10CMEJFA [DX3018]
R5F10CMELFA [DX3017]
R5F10CMFJFA [DX3018]
R5F10CMFLFA [DX3017]
R5F10CMGJFA [DX3018]
R5F10CMGLFA [DX3017]
R5F10CMHJFA [DX3018]
R5F10CMHLFA [DX3017]
R5F10CMJJFA [DX3018]
R5F10CMJLFA [DX3017]
R5F10CMKJFA [DX3018]
R5F10CMKLFA [DX3017]
R5F10CMLJFA [DX3018]
R5F10CMLLFA [DX3017]
R5F10CPCJFA [DX3062]
R5F10CPCLFA [DX3062]
R5F10CPDJFA [DX3062]
R5F10CPDLFA [DX3062]
R5F10CPEJFA [DX3062]
R5F10CPELFA [DX3062]
R5F10CPFJFA [DX3062]
R5F10CPFLFA [DX3062]
R5F10CPGJFA [DX3062]
R5F10CPGLFA [DX3062]
R5F10CPHJFA [DX3062]
R5F10CPHLFA [DX3062]
R5F10CPJJFA [DX3062]
R5F10CPJLFA [DX3062]
R5F10CPKJFA [DX3062]
R5F10CPKLFA [DX3062]
R5F10CPLJFA [DX3062]
R5F10CPLLFA [DX3062]
R5F10CSCJFB [DX3031]
R5F10CSDJFB [DX3031]
R5F10CSEJFB [DX3031]
R5F10CSFJFB [DX3031]
R5F10CSGJFB [DX3031]
R5F10CSHJFB [DX3031]
R5F10CSJJFB [DX3031]
R5F10CLKLFC [DX3085]
R5F10CLLJFA [DX3012]
R5F10CLLJFC [DX3085]
R5F10CLLLFA [DX3012]
R5F10CLLLFC [DX3085]
R5F10CMCJFB [DX3016]
R5F10CMCLFB [DX3016]
R5F10CMDJFB [DX3016]
R5F10CMDLFB [DX3016]
R5F10CMEJFB [DX3016]
R5F10CMELFB [DX3016]
R5F10CMFJFB [DX3016]
R5F10CMFLFB [DX3016]
R5F10CMGJFB [DX3016]
R5F10CMGLFB [DX3016]
R5F10CMHJFB [DX3016]
R5F10CMHLFB [DX3016]
R5F10CMJJFB [DX3016]
R5F10CMJLFB [DX3016]
R5F10CMKJFB [DX3016]
R5F10CMKLFB [DX3016]
R5F10CMLJFB [DX3016]
R5F10CMLLFB [DX3016]
R5F10CPCJFB [DX3021]
R5F10CPCLFB [DX3021]
R5F10CPDJFB [DX3021]
R5F10CPDLFB [DX3021]
R5F10CPEJFB [DX3021]
R5F10CPELFB [DX3021]
R5F10CPFJFB [DX3021]
R5F10CPFLFB [DX3021]
R5F10CPGJFB [DX3021]
R5F10CPGLFB [DX3021]
R5F10CPHJFB [DX3021]
R5F10CPHLFB [DX3021]
R5F10CPJJFB [DX3021]
R5F10CPJLFB [DX3021]
R5F10CPKJFB [DX3021]
R5F10CPKLFB [DX3021]
R5F10CPLJFB [DX3021]
R5F10CPLLFB [DX3021]
R5F10CSCLFB [DX3031]
R5F10CSDLFB [DX3031]
R5F10CSELFB [DX3031]
R5F10CSFLFB [DX3031]
R5F10CSGLFB [DX3031]
R5F10CSHLFB [DX3031]
R5F10CSJLFB [DX3031]

R5F10CSKJFB [DX3031]
R5F10CSLJFB [DX3031]
R5F10D6AJSP [DX1026]
R5F10D6CJSP [DX1026]
R5F10D6DJSP [DX1026]
R5F10D6EJSP [DX1026]
R5F10D6FJSP [DX1026]
R5F10D6GJSP [DX1026]
R5F10D6HJSP [DX1026]
R5F10D6JJSP [DX1026]
R5F10D6KJSP [DX1026]
R5F10D6LJSP [DX1026]
R5F10D7AJNA [DX4012]
R5F10D7CJNA [DX4012]
R5F10D7DJNA [DX4012]
R5F10D7EJNA [DX4012]
R5F10D7FJNA [DX4012]
R5F10D7GJNA [DX4012]
R5F10D7HJNA [DX4012]
R5F10D7JJNA [DX4012]
R5F10D7KJNA [DX4012]
R5F10D7LJNA [DX4012]
R5F10D8AJLA [DX0001]
R5F10D8CJLA [DX0001]
R5F10D8DJLA [DX0001]
R5F10D8EJLA [DX0001]
R5F10D8FJLA [DX0001]
R5F10D8GJLA [DX0001]
R5F10D8HJLA [DX0001]
R5F10D8JJLA [DX0001]
R5F10D8KJLA [DX0001]
R5F10D8LJLA [DX0001]
R5F10DAAJSP [DX1087]
R5F10DACJSP [DX1087]
R5F10DADJSP [DX1087]
R5F10DAEJSP [DX1087]
R5F10DAFJSP [DX1087]
R5F10DAGJSP [DX1087]
R5F10DAHJSP [DX1087]
R5F10DAJJSP [DX1087]
R5F10DAKJSP [DX1087]
R5F10DALJSP [DX1087]
R5F10DBAJNA [DX4015]
R5F10DBCJNA [DX4015]
R5F10DBDJNA [DX4015]
R5F10DBEJNA [DX4015]
R5F10DBFJNA [DX4015]
R5F10DBGJNA [DX4015]
R5F10CSKLFB [DX3031]
R5F10CSLLFB [DX3031]
R5F10D6ALSP [DX1026]
R5F10D6CLSP [DX1026]
R5F10D6DLSP [DX1026]
R5F10D6ELSP [DX1026]
R5F10D6FLSP [DX1026]
R5F10D6GLSP [DX1026]
R5F10D6HLSP [DX1026]
R5F10D6JLSP [DX1026]
R5F10D6KLSP [DX1026]
R5F10D6LLSP [DX1026]
R5F10D7ALNA [DX4012]
R5F10D7CLNA [DX4012]
R5F10D7DLNA [DX4012]
R5F10D7ELNA [DX4012]
R5F10D7FLNA [DX4012]
R5F10D7GLNA [DX4012]
R5F10D7HLNA [DX4012]
R5F10D7JLNA [DX4012]
R5F10D7KLNA [DX4012]
R5F10D7LLNA [DX4012]
R5F10D8ALLA [DX0001]
R5F10D8CLLA [DX0001]
R5F10D8DLLA [DX0001]
R5F10D8ELLA [DX0001]
R5F10D8FLLA [DX0001]
R5F10D8GLLA [DX0001]
R5F10D8HLLA [DX0001]
R5F10D8JLLA [DX0001]
R5F10D8KLLA [DX0001]
R5F10D8LLLA [DX0001]
R5F10DAALSP [DX1087]
R5F10DACLSP [DX1087]
R5F10DADLSP [DX1087]
R5F10DAELSP [DX1087]
R5F10DAFLSP [DX1087]
R5F10DAGLSP [DX1087]
R5F10DAHLSP [DX1087]
R5F10DAJLSP [DX1087]
R5F10DAKLSP [DX1087]
R5F10DALLSP [DX1087]
R5F10DBALNA [DX4015]
R5F10DBCLNA [DX4015]
R5F10DBDLNA [DX4015]
R5F10DBELNA [DX4015]
R5F10DBFLNA [DX4015]
R5F10DBGLNA [DX4015]

R5F10DBHJNA [DX4015]	R5F10DBHLNA [DX4015]
R5F10DBJJNA [DX4015]	R5F10DBJLNA [DX4015]
R5F10DBKJNA [DX4015]	R5F10DBKLNA [DX4015]
R5F10DBLJNA [DX4015]	R5F10DBLLNA [DX4015]
R5F10DCAJLA [DX0001]	R5F10DCALLA [DX0001]
R5F10DCCJLA [DX0001]	R5F10DCCLLA [DX0001]
R5F10DCDJLA [DX0001]	R5F10DCDLLA [DX0001]
R5F10DCEJLA [DX0001]	R5F10DCELLA [DX0001]
R5F10DCFJLA [DX0001]	R5F10DCFLLA [DX0001]
R5F10DCGJLA [DX0001]	R5F10DCGLLA [DX0001]
R5F10DCHJLA [DX0001]	R5F10DCHLLA [DX0001]
R5F10DCJJLA [DX0001]	R5F10DCJLLA [DX0001]
R5F10DCKJLA [DX0001]	R5F10DCKLLA [DX0001]
R5F10DCLJLA [DX0001]	R5F10DCLLLA [DX0001]
R5F10DEAJNA [DX4017]	R5F10DEALNA [DX4017]
R5F10DECJNA [DX4017]	R5F10DECLNA [DX4017]
R5F10DEDJNA [DX4017]	R5F10DEDLNA [DX4017]
R5F10DEEJNA [DX4017]	R5F10DEELNA [DX4017]
R5F10DEFJNA [DX4017]	R5F10DEFLNA [DX4017]
R5F10DEGJNA [DX4017]	R5F10DEGLNA [DX4017]
R5F10DEHJNA [DX4017]	R5F10DEHLNA [DX4017]
R5F10DEJJNA [DX4017]	R5F10DEJLNA [DX4017]
R5F10DEKJNA [DX4017]	R5F10DEKLNA [DX4017]
R5F10DELJNA [DX4017]	R5F10DELLNA [DX4017]
R5F10DFAJFP [DX3005]	R5F10DFALFP [DX3005]
R5F10DFCJFP [DX3005]	R5F10DFCLFP [DX3005]
R5F10DFDJFP [DX3005]	R5F10DFDLFP [DX3005]
R5F10DFEJFP [DX3005]	R5F10DFELFP [DX3005]
R5F10DFFJFP [DX3005]	R5F10DFFLFP [DX3005]
R5F10DFGJFP [DX3005]	R5F10DFGLFP [DX3005]
R5F10DFHJFP [DX3005]	R5F10DFHLFP [DX3005]
R5F10DFJJFP [DX3005]	R5F10DFJLFP [DX3005]
R5F10DFKJFP [DX3005]	R5F10DFKLFP [DX3005]
R5F10DFLJFP [DX3005]	R5F10DFLLFP [DX3005]
R5F10DGAJFB [DX3007]	R5F10DGAJNA [DX4021]
R5F10DGALFB [DX3007]	R5F10DGALNA [DX4021]
R5F10DGCJFB [DX3007]	R5F10DGCJNA [DX4021]
R5F10DGCLFB [DX3007]	R5F10DGCLNA [DX4021]
R5F10DGDJFB [DX3007]	R5F10DGDJNA [DX4021]
R5F10DGDLFB [DX3007]	R5F10DGDLNA [DX4021]
R5F10DGEJFB [DX3007]	R5F10DGEJNA [DX4021]
R5F10DGELFB [DX3007]	R5F10DGELNA [DX4021]
R5F10DGFJFB [DX3007]	R5F10DGFJNA [DX4021]
R5F10DGFLFB [DX3007]	R5F10DGFLNA [DX4021]
R5F10DGGJFB [DX3007]	R5F10DGGJNA [DX4021]
R5F10DGGLFB [DX3007]	R5F10DGGLNA [DX4021]
R5F10DGHJFB [DX3007]	R5F10DGHJNA [DX4021]
R5F10DGHLFB [DX3007]	R5F10DGHLNA [DX4021]

R5F10DGJJFB [DX3007]
R5F10DGJLFB [DX3007]
R5F10DGKJFB [DX3007]
R5F10DGKLFB [DX3007]
R5F10DGLJFB [DX3007]
R5F10DGLLFB [DX3007]
R5F10DJCJFA [DX3010]
R5F10DJDJFA [DX3010]
R5F10DJEJFA [DX3010]
R5F10DJFJFA [DX3010]
R5F10DJGJFA [DX3010]
R5F10DJHJFA [DX3010]
R5F10DJJJFA [DX3010]
R5F10DJKJFA [DX3010]
R5F10DJLJFA [DX3010]
R5F10DLCJBG [DX0001]
R5F10DLCJFB [DX3011]
R5F10DLCLBG [DX0001]
R5F10DLCLFB [DX3011]
R5F10DLDJBG [DX0001]
R5F10DLDJFB [DX3011]
R5F10DLDLBG [DX0001]
R5F10DLDLFB [DX3011]
R5F10DLEJBG [DX0001]
R5F10DLEJFB [DX3011]
R5F10DLELBG [DX0001]
R5F10DLELFB [DX3011]
R5F10DLFJBG [DX0001]
R5F10DLFJFB [DX3011]
R5F10DLFLBG [DX0001]
R5F10DLFLFB [DX3011]
R5F10DLGJBG [DX0001]
R5F10DLGJFB [DX3011]
R5F10DLGLBG [DX0001]
R5F10DLGLFB [DX3011]
R5F10DLHJBG [DX0001]
R5F10DLHJFB [DX3011]
R5F10DLHLBG [DX0001]
R5F10DLHLFB [DX3011]
R5F10DLJJBG [DX0001]
R5F10DLJJFB [DX3011]
R5F10DLJLBG [DX0001]
R5F10DLJLFB [DX3011]
R5F10DLKJBG [DX0001]
R5F10DLKJFB [DX3011]
R5F10DLKLBG [DX0001]
R5F10DLKLFB [DX3011]
R5F10DLLJBG [DX0001]
R5F10DGJJNA [DX4021]
R5F10DGJLNA [DX4021]
R5F10DGKJNA [DX4021]
R5F10DGKLNA [DX4021]
R5F10DGLJNA [DX4021]
R5F10DGLLNA [DX4021]
R5F10DJCLFA [DX3010]
R5F10DJDLFA [DX3010]
R5F10DJELFA [DX3010]
R5F10DJFLFA [DX3010]
R5F10DJGLFA [DX3010]
R5F10DJHLFA [DX3010]
R5F10DJJLFA [DX3010]
R5F10DJKLFA [DX3010]
R5F10DJLLFA [DX3010]
R5F10DLCJFA [DX3012]
R5F10DLCJFC [DX3085]
R5F10DLCLFA [DX3012]
R5F10DLCLFC [DX3085]
R5F10DLDJFA [DX3012]
R5F10DLDJFC [DX3085]
R5F10DLDLFA [DX3012]
R5F10DLDLFC [DX3085]
R5F10DLEJFA [DX3012]
R5F10DLEJFC [DX3085]
R5F10DLELFA [DX3012]
R5F10DLELFC [DX3085]
R5F10DLFJFA [DX3012]
R5F10DLFJFC [DX3085]
R5F10DLFLFA [DX3012]
R5F10DLFLFC [DX3085]
R5F10DLGJFA [DX3012]
R5F10DLGJFC [DX3085]
R5F10DLGLFA [DX3012]
R5F10DLGLFC [DX3085]
R5F10DLHJFA [DX3012]
R5F10DLHJFC [DX3085]
R5F10DLHLFA [DX3012]
R5F10DLHLFC [DX3085]
R5F10DLJJFA [DX3012]
R5F10DLJJFC [DX3085]
R5F10DLJLFA [DX3012]
R5F10DLJLFC [DX3085]
R5F10DLKJFA [DX3012]
R5F10DLKJFC [DX3085]
R5F10DLKLFA [DX3012]
R5F10DLKLFC [DX3085]
R5F10DLLJFA [DX3012]

R5F10DLLJFB [DX3011]
R5F10DLLLBG [DX0001]
R5F10DLLLFB [DX3011]
R5F10DMCJFA [DX3017]
R5F10DMCLFA [DX3017]
R5F10DMDJFA [DX3017]
R5F10DMDLFA [DX3017]
R5F10DMEJFA [DX3017]
R5F10DMELFA [DX3017]
R5F10DMFJFA [DX3017]
R5F10DMFLFA [DX3017]
R5F10DMGJFA [DX3017]
R5F10DMGLFA [DX3017]
R5F10DMHJFA [DX3017]
R5F10DMHLFA [DX3017]
R5F10DMJJFA [DX3017]
R5F10DMJLFA [DX3017]
R5F10DMKJFA [DX3017]
R5F10DMKLFA [DX3017]
R5F10DMLJFA [DX3017]
R5F10DMLLFA [DX3017]
R5F10DPCJFA [DX3062]
R5F10DPCLFA [DX3062]
R5F10DPDJFA [DX3062]
R5F10DPDLFA [DX3062]
R5F10DPEJFA [DX3062]
R5F10DPELFA [DX3062]
R5F10DPFJFA [DX3062]
R5F10DPFLFA [DX3062]
R5F10DPGJFA [DX3062]
R5F10DPGLFA [DX3062]
R5F10DPHJFA [DX3062]
R5F10DPHLFA [DX3062]
R5F10DPJJFA [DX3062]
R5F10DPJLFA [DX3062]
R5F10DPKJFA [DX3062]
R5F10DPKLFA [DX3062]
R5F10DPLJFA [DX3062]
R5F10DPLLFA [DX3062]
R5F10DSCJFB [DX3031]
R5F10DSDJFB [DX3031]
R5F10DSEJFB [DX3031]
R5F10DSFJFB [DX3031]
R5F10DSGJFB [DX3031]
R5F10DSHJFB [DX3031]
R5F10DSJJFB [DX3031]
R5F10DSKJFB [DX3031]
R5F10DSLJFB [DX3031]
R5F10DLLJFC [DX3085]
R5F10DLLLFA [DX3012]
R5F10DLLLFC [DX3085]
R5F10DMCJFB [DX3016]
R5F10DMCLFB [DX3016]
R5F10DMDJFB [DX3016]
R5F10DMDLFB [DX3016]
R5F10DMEJFB [DX3016]
R5F10DMELFB [DX3016]
R5F10DMFJFB [DX3016]
R5F10DMFLFB [DX3016]
R5F10DMGJFB [DX3016]
R5F10DMGLFB [DX3016]
R5F10DMHJFB [DX3016]
R5F10DMHLFB [DX3016]
R5F10DMJJFB [DX3016]
R5F10DMJLFB [DX3016]
R5F10DMKJFB [DX3016]
R5F10DMKLFB [DX3016]
R5F10DMLJFB [DX3016]
R5F10DMLLFB [DX3016]
R5F10DPCJFB [DX3021]
R5F10DPCLFB [DX3021]
R5F10DPDJFB [DX3021]
R5F10DPDLFB [DX3021]
R5F10DPEJFB [DX3021]
R5F10DPELFB [DX3021]
R5F10DPFJFB [DX3021]
R5F10DPFLFB [DX3021]
R5F10DPGJFB [DX3021]
R5F10DPGLFB [DX3021]
R5F10DPHJFB [DX3021]
R5F10DPHLFB [DX3021]
R5F10DPJJFB [DX3021]
R5F10DPJLFB [DX3021]
R5F10DPKJFB [DX3021]
R5F10DPKLFB [DX3021]
R5F10DPLJFB [DX3021]
R5F10DPLLFB [DX3021]
R5F10DSCLFB [DX3031]
R5F10DSDLFB [DX3031]
R5F10DSELFB [DX3031]
R5F10DSFLFB [DX3031]
R5F10DSGLFB [DX3031]
R5F10DSHLFB [DX3031]
R5F10DSJLFB [DX3031]
R5F10DSKLFB [DX3031]
R5F10DSLLFB [DX3031]

R5F10WLAAFA [DX3012]
R5F10WLAAFB [DX3011]
R5F10WLAGFA [DX3012]
R5F10WLAGFB [DX3011]
R5F10WLBAFA [DX3012]
R5F10WLBAFB [DX3011]
R5F10WLBGFA [DX3012]
R5F10WLBGFB [DX3011]
R5F10WLCAFA [DX3012]
R5F10WLCAFB [DX3011]
R5F10WLCGFA [DX3012]
R5F10WLCGFB [DX3011]
R5F10WLDAFA [DX3012]
R5F10WLDAFB [DX3011]
R5F10WLDGFA [DX3012]
R5F10WLDGFB [DX3011]
R5F10WLEAFA [DX3012]
R5F10WLEAFB [DX3011]
R5F10WLEGFA [DX3012]
R5F10WLEGFB [DX3011]
R5F10WLFAFA [DX3012]
R5F10WLFAFB [DX3011]
R5F10WLFGFA [DX3012]
R5F10WLFGFB [DX3011]
R5F10WLGAFA [DX3012]
R5F10WLGAFB [DX3011]
R5F10WLGGFA [DX3012]
R5F10WLGGFB [DX3011]
R5F10WMAAFA [DX3017]
R5F10WMAAFB [DX3016]
R5F10WMAGFA [DX3017]
R5F10WMAGFB [DX3016]
R5F10WMBAFA [DX3017]
R5F10WMBAFB [DX3016]
R5F10WMBGFA [DX3017]
R5F10WMBGFB [DX3016]
R5F10WMCAFA [DX3017]
R5F10WMCAFB [DX3016]
R5F10WMCGFA [DX3017]
R5F10WMCGFB [DX3016]
R5F10WMDAFA [DX3017]
R5F10WMDAFB [DX3016]
R5F10WMDGFA [DX3017]
R5F10WMDGFB [DX3016]
R5F10WMEAFA [DX3017]
R5F10WMEAFB [DX3016]
R5F10WMEGFA [DX3017]
R5F10WMEGFB [DX3016]
R5F10WMFAFA [DX3017]
R5F10WMFAFB [DX3016]
R5F10WMFGFA [DX3017]
R5F10WMFGFB [DX3016]
R5F10WMGAFA [DX3017]
R5F10WMGAFB [DX3016]
R5F10WMGGFA [DX3017]
R5F10WMGGFB [DX3016]
R5F10Y14ASP [DX1001]
R5F10Y16ASP [DX1001]
R5F10Y17ASP [DX1001]
R5F10Y44ASP [DX1001]
R5F10Y46ASP [DX1001]
R5F10Y47ASP [DX1001]
R7F01592ESN [DX1033]
R7F01692ESN [DX1033]
R7F0C001G2DFB [DX3007]
R7F0C001L2DFB [DX3011]
R7F0C002G2DFB [DX3007]
R7F0C002L2DFB [DX3011]
R7F0C003M2DFB [DX3016]
R7F0C004M2DFB [DX3016]
R7F0C008A2DSP [DX1026]
R7F0C008B2DFP [DX3001]
R7F0C008F2DFP [DX3005]
R7F0C009A2DSP [DX1026]
R7F0C009B2DFP [DX3001]
R7F0C009F2DFP [DX3005]
R7F0C011B2001DFP [DX3001]
R7F0C012B2001DFP [DX3001]
R7F0C013B2001DFP [DX3001]
R7F0C014 [DX3001]
R7F0C019L2DFB [DX3011]
R7F0C903 [DX3001]
R7F0C904 [DX3001]
R7F0C905 [DX3001]
R7F0C906 [DX3001]
R7F0C907 [DX3001]
R7F0C908 [DX3001]
uPD70F3003@TQFP100 [DX3043]
uPD70F3003A@TQFP100 [DX3043]
uPD70F3025@TQFP100 [DX3043]
uPD70F3025A@TQFP100 [DX3043]
uPD70F3102 [DX3035]
uPD70F3102A [DX3035]
uPD70F3102B [DX3035]
uPD70F3107@LQFP144 [DX3035]
uPD70F3107A@LQFP144 [DX3035]

uPD70F3107B@LQFP144 [DX3035]
uPD70F3114GC [DX3021]
uPD70F3114GK [DX3023]
uPD70F3116GC [DX3021]
uPD70F3116GK [DX3023]
UPD70F3329GC [DX3014]
uPD70F3333GC [DX3043]
uPD70F3333GCA [DX3043]
uPD70F3334GC [DX3043]
uPD70F3334GCA [DX3043]
uPD70F3335GC [DX3043]
uPD70F3335GCA [DX3043]
uPD70F3336GC [DX3043]
uPD70F3336GCA [DX3043]
uPD70F3340GC [DX3043]
uPD70F3340GCA [DX3043]
uPD70F3340GJ@LQFP144 [DX3051]
uPD70F3340GJ@LQFP144(Uart) [DX3051]
uPD70F3340GJA@LQFP144 [DX3051]
uPD70F3340GJA@LQFP144(Uart) [DX3051]
uPD70F3341GC [DX3043]
uPD70F3341GCA [DX3043]
uPD70F3341GJ@LQFP144 [DX3051]
uPD70F3341GJ@LQFP144(Uart) [DX3051]
uPD70F3341GJA@LQFP144 [DX3051]
uPD70F3341GJA@LQFP144(Uart) [DX3051]
uPD70F3342GC [DX3043]
uPD70F3342GCA [DX3043]
uPD70F3342GJ@LQFP144 [DX3051]
uPD70F3342GJ@LQFP144(Uart) [DX3051]
uPD70F3342GJA@LQFP144 [DX3051]
uPD70F3342GJA@LQFP144(Uart) [DX3051]
uPD70F3343GC [DX3043]
uPD70F3343GCA [DX3043]
uPD70F3343GJ@LQFP144 [DX3051]
uPD70F3343GJ@LQFP144(Uart) [DX3051]
uPD70F3343GJA@LQFP144 [DX3051]
uPD70F3343GJA@LQFP144(Uart) [DX3051]
uPD70F3344GJ@LQFP144 [DX3051]
uPD70F3344GJ@LQFP144(Uart) [DX3051]
uPD70F3344GJA@LQFP144 [DX3051]
uPD70F3344GJA@LQFP144(Uart) [DX3051]
uPD70F3345GJ@LQFP144 [DX3051]
uPD70F3345GJ@LQFP144(Uart) [DX3051]
uPD70F3345GJA@LQFP144 [DX3051]
uPD70F3345GJA@LQFP144(Uart) [DX3051]
uPD70F3346GJ@LQFP144 [DX3051]
uPD70F3346GJ@LQFP144(Uart) [DX3051]
uPD70F3346GJA@LQFP144 [DX3051]
uPD70F3346GJA@LQFP144(Uart) [DX3051]
uPD70F3347GJ@LQFP144 [DX3051]
uPD70F3347GJ@LQFP144(Uart) [DX3051]
uPD70F3347GJA@LQFP144 [DX3051]
uPD70F3347GJA@LQFP144(Uart) [DX3051]
uPD70F3348GJ@LQFP144 [DX3051]
uPD70F3348GJ@LQFP144(Uart) [DX3051]
uPD70F3348GJA@LQFP144 [DX3051]
uPD70F3348GJA@LQFP144(Uart) [DX3051]
uPD70F3350GC [DX3043]
uPD70F3350GCA [DX3043]

uPD70F3350GJ@LQFP144 [DX3051]
uPD70F3350GJ@LQFP144(Uart) [DX3051]
uPD70F3350GJA@LQFP144 [DX3051]
uPD70F3350GJA@LQFP144(Uart) [DX3051]
uPD70F3351GC [DX3043]　　uPD70F3351GCA [DX3043]
uPD70F3351GJ@LQFP144 [DX3051]
uPD70F3351GJ@LQFP144(Uart) [DX3051]
uPD70F3351GJA@LQFP144 [DX3051]
uPD70F3351GJA@LQFP144(Uart) [DX3051]
uPD70F3352GC [DX3043]　　uPD70F3352GCA [DX3043]
uPD70F3352GJ@LQFP144 [DX3051]
uPD70F3352GJ@LQFP144(Uart) [DX3051]
uPD70F3352GJA@LQFP144 [DX3051]
uPD70F3352GJA@LQFP144(Uart) [DX3051]
uPD70F3353GC [DX3043]　　uPD70F3353GCA [DX3043]
uPD70F3353GJ@LQFP144 [DX3051]
uPD70F3353GJ@LQFP144(Uart) [DX3051]
uPD70F3353GJA@LQFP144 [DX3051]
uPD70F3353GJA@LQFP144(Uart) [DX3051]
uPD70F3354GJ@LQFP144 [DX3051]
uPD70F3354GJ@LQFP144(Uart) [DX3051]
uPD70F3354GJA@LQFP144 [DX3051]
uPD70F3354GJA@LQFP144(Uart) [DX3051]
uPD70F3355GJ@LQFP144 [DX3051]
uPD70F3355GJ@LQFP144(Uart) [DX3051]
uPD70F3355GJA@LQFP144 [DX3051]
uPD70F3355GJA@LQFP144(Uart) [DX3051]
uPD70F3356GJ@LQFP144 [DX3051]
uPD70F3356GJ@LQFP144(Uart) [DX3051]
uPD70F3356GJA@LQFP144 [DX3051]
uPD70F3356GJA@LQFP144(Uart) [DX3051]
uPD70F3357GJ@LQFP144 [DX3051]
uPD70F3357GJ@LQFP144(Uart) [DX3051]
uPD70F3357GJA@LQFP144 [DX3051]
uPD70F3357GJA@LQFP144(Uart) [DX3051]
uPD70F3358GJ@LQFP144 [DX3051]
uPD70F3358GJ@LQFP144(Uart) [DX3051]
uPD70F3358GJA@LQFP144 [DX3051]
uPD70F3358GJA@LQFP144(Uart) [DX3051]
uPD70F3360GJ@LQFP144 [DX3051]
uPD70F3360GJ@LQFP144(Uart) [DX3051]
uPD70F3360GJA@LQFP144 [DX3051]
uPD70F3360GJA@LQFP144(Uart) [DX3051]
uPD70F3361GJ@LQFP144 [DX3051]
uPD70F3361GJ@LQFP144(Uart) [DX3051]
uPD70F3361GJA@LQFP144 [DX3051]
uPD70F3361GJA@LQFP144(Uart) [DX3051]
uPD70F3362GJ@LQFP144 [DX3051]

uPD70F3362GJ@LQFP144(Uart) [DX3051]
uPD70F3362GJA@LQFP144 [DX3051]
uPD70F3362GJA@LQFP144(Uart) [DX3051]
uPD70F3363GJ@LQFP144 [DX3051]
uPD70F3363GJ@LQFP144(Uart) [DX3051]
uPD70F3363GJA@LQFP144 [DX3051]
uPD70F3363GJA@LQFP144(Uart) [DX3051]
uPD70F3364GJ@LQFP144 [DX3051]
uPD70F3364GJ@LQFP144(Uart) [DX3051]
uPD70F3364GJA@LQFP144 [DX3051]
uPD70F3364GJA@LQFP144(Uart) [DX3051]
uPD70F3365GJ@LQFP144 [DX3051]
uPD70F3365GJ@LQFP144(Uart) [DX3051]
uPD70F3365GJA@LQFP144 [DX3051]
uPD70F3365GJA@LQFP144(Uart) [DX3051]
uPD70F3366GJ@LQFP144 [DX3051]
uPD70F3366GJ@LQFP144(Uart) [DX3051]
uPD70F3366GJA@LQFP144 [DX3051]
uPD70F3366GJA@LQFP144(Uart) [DX3051]
uPD70F3367GJ@LQFP144 [DX3051]
uPD70F3367GJ@LQFP144(Uart) [DX3051]
uPD70F3367GJA@LQFP144 [DX3051]
uPD70F3367GJA@LQFP144(Uart) [DX3051]
uPD70F3368GJ@LQFP144 [DX3051]
uPD70F3368GJ@LQFP144(Uart) [DX3051]
uPD70F3368GJA@LQFP144 [DX3051]
uPD70F3368GJA@LQFP144(Uart) [DX3051]

uPD70F3370 [DX3011]	uPD70F3371 [DX3011]
uPD70F3372 [DX3016]	uPD70F3373 [DX3016]
uPD70F3374 [DX3043]	uPD70F3375 [DX3043]
uPD70F3376 [DX3043]	uPD70F3377 [DX3043]
uPD70F3378 [DX3051]	uPD70F3379 [DX3051]
uPD70F3380 [DX3051]	uPD70F3381 [DX3051]
uPD70F3382 [DX3051]	uPD70F3383 [DX0001]
uPD70F3384 [DX0001]	uPD70F3385 [DX0001]
uPD70F3421AGJU [DX3051]	uPD70F3421GJU [DX3051]
uPD70F3422AGJU [DX3051]	uPD70F3422GJU [DX3051]
uPD70F3423AGJU [DX3051]	uPD70F3423GJU [DX3051]
uPD70F3424AGJU [DX3051]	uPD70F3424GJU [DX3051]
uPD70F3425AGJU [DX3051]	uPD70F3425GJU [DX3051]
uPD70F3426AGJU [DX3051]	uPD70F3426GJU [DX3051]
uPD70F3427AGDU [DX0001]	uPD70F3427GDU [DX0001]
uPD70F3451GC [DX3018]	uPD70F3452GC [DX3018]
uPD70F3453GC@LQFP100 [DX3043]	uPD70F3453GF@LQFP100 [DX3062]
uPD70F3454GC@LQFP100 [DX3043]	uPD70F3454GF@LQFP100 [DX3062]
uPD70F3455GC [DX3018]	uPD70F3456GC [DX3018]
uPD70F3610M1GAA [DX3085]	uPD70F3610M1GAA1 [DX3085]
uPD70F3610M1GAA2 [DX3085]	uPD70F3610M1GBA [DX3011]

uPD70F3610M1GBA1 [DX3011]
uPD70F3610M1GBA2 [DX3011]
uPD70F3610M2GAA [DX3085]
uPD70F3610M2GAA1 [DX3085]
uPD70F3610M2GAA2 [DX3085]
uPD70F3610M2GBA [DX3011]
uPD70F3610M2GBA1 [DX3011]
uPD70F3610M2GBA2 [DX3011]
uPD70F3611M1GAA [DX3085]
uPD70F3611M1GAA1 [DX3085]
uPD70F3611M1GAA2 [DX3085]
uPD70F3611M1GBA [DX3011]
uPD70F3611M1GBA1 [DX3011]
uPD70F3611M1GBA2 [DX3011]
uPD70F3611M2GAA [DX3085]
uPD70F3611M2GAA1 [DX3085]
uPD70F3611M2GAA2 [DX3085]
uPD70F3611M2GBA [DX3011]
uPD70F3611M2GBA1 [DX3011]
uPD70F3611M2GBA2 [DX3011]
uPD70F3612M1GAA [DX3085]
uPD70F3612M1GAA1 [DX3085]
uPD70F3612M1GAA2 [DX3085]
uPD70F3612M1GBA [DX3011]
uPD70F3612M1GBA1 [DX3011]
uPD70F3612M1GBA2 [DX3011]
uPD70F3612M2GAA [DX3085]
uPD70F3612M2GAA1 [DX3085]
uPD70F3612M2GAA2 [DX3085]
uPD70F3612M2GBA [DX3011]
uPD70F3612M2GBA1 [DX3011]
uPD70F3612M2GBA2 [DX3011]
uPD70F3613M1GAA [DX3085]
uPD70F3613M1GAA1 [DX3085]
uPD70F3613M1GAA2 [DX3085]
uPD70F3613M1GBA [DX3011]
uPD70F3613M1GBA1 [DX3011]
uPD70F3613M1GBA2 [DX3011]
uPD70F3613M2GAA [DX3085]
uPD70F3613M2GAA1 [DX3085]
uPD70F3613M2GAA2 [DX3085]
uPD70F3613M2GBA [DX3011]
uPD70F3613M2GBA1 [DX3011]
uPD70F3613M2GBA2 [DX3011]
uPD70F3614M1GAA [DX3085]
uPD70F3614M1GAA1 [DX3085]
uPD70F3614M1GAA2 [DX3085]
uPD70F3614M1GBA [DX3011]
uPD70F3614M1GBA1 [DX3011]
uPD70F3614M1GBA2 [DX3011]
uPD70F3614M2GAA [DX3085]
uPD70F3614M2GAA1 [DX3085]
uPD70F3614M2GAA2 [DX3085]
uPD70F3614M2GBA [DX3011]
uPD70F3614M2GBA1 [DX3011]
uPD70F3614M2GBA2 [DX3011]
uPD70F3615M1GBA [DX3016]
uPD70F3615M1GBA1 [DX3016]
uPD70F3615M1GBA2 [DX3016]
uPD70F3615M2GBA [DX3016]
uPD70F3615M2GBA1 [DX3016]
uPD70F3615M2GBA2 [DX3016]
uPD70F3616M1GBA [DX3016]
uPD70F3616M1GBA1 [DX3016]
uPD70F3616M1GBA2 [DX3016]
uPD70F3616M2GBA [DX3016]
uPD70F3616M2GBA1 [DX3016]
uPD70F3616M2GBA2 [DX3016]
uPD70F3617M1GBA [DX3016]
uPD70F3617M1GBA1 [DX3016]
uPD70F3617M1GBA2 [DX3016]
uPD70F3617M2GBA [DX3016]
uPD70F3617M2GBA1 [DX3016]
uPD70F3617M2GBA2 [DX3016]
uPD70F3618M1GBA [DX3016]
uPD70F3618M1GBA1 [DX3016]
uPD70F3618M1GBA2 [DX3016]
uPD70F3618M2GBA [DX3016]
uPD70F3618M2GBA1 [DX3016]
uPD70F3618M2GBA2 [DX3016]
uPD70F3619M1GBA [DX3016]
uPD70F3619M1GBA1 [DX3016]
uPD70F3619M1GBA2 [DX3016]
uPD70F3619M2GBA [DX3016]
uPD70F3619M2GBA1 [DX3016]
uPD70F3619M2GBA2 [DX3016]
uPD70F3620M1GBA [DX3043]
uPD70F3620M1GBA1 [DX3043]
uPD70F3620M1GBA2 [DX3043]
uPD70F3620M2GBA [DX3043]
uPD70F3620M2GBA1 [DX3043]
uPD70F3620M2GBA2 [DX3043]
uPD70F3621M1GBA [DX3043]
uPD70F3621M1GBA1 [DX3043]
uPD70F3621M1GBA2 [DX3043]
uPD70F3621M2GBA [DX3043]

uPD70F3621M2GBA1 [DX3043]
uPD70F3621M2GBA2 [DX3043]
uPD70F3622M1GBA [DX3043]
uPD70F3622M1GBA1 [DX3043]
uPD70F3622M1GBA2 [DX3043]
uPD70F3622M2GBA [DX3043]
uPD70F3622M2GBA1 [DX3043]
uPD70F3622M2GBA2 [DX3043]
uPD70F3623 [DX3011]
uPD70F3623(data flash) [DX3011]
uPD70F3623GK [DX3011]
uPD70F3623GK(data flash) [DX3011]
uPD70F3624 [DX3011]
uPD70F3624(data flash) [DX3011]
uPD70F3624GK [DX3011]
uPD70F3624GK(data flash) [DX3011]
uPD70F3625 [DX3016]
uPD70F3625(data flash) [DX3016]
uPD70F3625GK [DX3016]
uPD70F3625GK(data flash) [DX3016]
uPD70F3626 [DX3016]
uPD70F3626(data flash) [DX3016]
uPD70F3626GK [DX3016]
uPD70F3626GK(data flash) [DX3016]
uPD70F3627 [DX3043]
uPD70F3627(data flash) [DX3043]
uPD70F3627GK [DX3043]
uPD70F3627GK(data flash) [DX3043]
uPD70F3628 [DX3043]
uPD70F3628(data flash) [DX3043]
uPD70F3628GK [DX3043]
uPD70F3628GK(data flash) [DX3043]
uPD70F3629 [DX3043]
uPD70F3629(data flash) [DX3043]
uPD70F3629GK [DX3043]
uPD70F3629GK(data flash) [DX3043]
uPD70F3630 [DX3043]
uPD70F3630(data flash) [DX3043]
uPD70F3630GK [DX3043]
uPD70F3630GK(data flash) [DX3043]
uPD70F3631 [DX3051]
uPD70F3631(data flash) [DX3051]
uPD70F3631GK [DX3051]
uPD70F3631GK(data flash) [DX3051]
uPD70F3632 [DX3051]
uPD70F3632(data flash) [DX3051]
uPD70F3632GK [DX3051]
uPD70F3632GK(data flash) [DX3051]
uPD70F3633 [DX3051]
uPD70F3633(data flash) [DX3051]
uPD70F3633GK [DX3051]
uPD70F3633GK(data flash) [DX3051]
uPD70F3634 [DX3051]
uPD70F3634(data flash) [DX3051]
uPD70F3634GK [DX3051]
uPD70F3634GK(data flash) [DX3051]
uPD70F3635 [DX3051]
uPD70F3635(data flash) [DX3051]
uPD70F3635GK [DX3051]
uPD70F3635GK(data flash) [DX3051]
uPD70F3742GJA [DX3051]
uPD70F3743GJA [DX3051]
uPD70F3744GJA [DX3051]
uPD70F3745GJA [DX3051]
uPD70F3746GJA [DX3051]
uPD70P3000@QFP100 [DX3043]
uPD70P3002@QFP100 [DX3043]
uPD75P0016@SDIP42 [DX0042]
uPD75P0016@TQFP44 [DX3066]
uPD75P0016CU@SDIP42 [DX0042]

uPD75P0016GB@TQFP44 [DX3002]
uPD75P0076GT@SOP42 [DX0001]
uPD75P008GB@TQFP44 [DX3002]
uPD75P108BDW [DX0064]
uPD75P108CW@SDIP64 [DX0064]
uPD75P108GF@PQFP64 [DX3015]
uPD75P116BDW [DX0064]
uPD75P116CW@SDIP64 [DX0064]
uPD75P116GF@PQFP64 [DX3015]
uPD75P218CW@SDIP64 [DX0064]
uPD75P3018AGK@TQFP80 [DX3016]
uPD75P3018GK@TQFP80 [DX3016]
uPD75P3036AGK@TQFP80 [DX3016]
uPD75P3036GK@TQFP80 [DX3016]
uPD75P308BGC@PQFP80 [DX3018]
uPD75P308GC [DX3018]
uPD75P308GK [DX3016]
uPD75P316BGC@PQFP80 [DX3018]
uPD75P316GC [DX3018]
uPD75P316GK [DX3016]
uPD75P54G@SOP20 [DX1026]
uPD75P64G@SOP20 [DX1026]
UPD76F0168GC [DX3014]
UPD76F9108GC [DX3014]
uPD78CP18CW [DX0064]
uPD78CP18CW(B) [DX0064]
uPD78CP18DW(A) [DX0064]
uPD78CP18GQ [DX0065]
uPD78CP18GQ(B) [DX0065]
uPD78F0034AGB [DX3011]
uPD78F0034AGK [DX3012]
uPD78F0034AYGB [DX3011]
uPD78F0034AYGK [DX3012]
uPD78F0034BGB [DX3011]
uPD78F0034BGK [DX3012]
uPD78F0034BYGB [DX3011]
uPD78F0034BYGK [DX3012]
uPD78F0034GB [DX3011]
uPD78F0034GK [DX3012]
uPD78F0101HMC(A1)@SSOP30 [DX1027]
uPD78F0101HMC@SSOP30 [DX1027]
uPD78F0102HMC(A1)@SSOP30 [DX1027]
uPD78F0102HMC@SSOP30 [DX1027]
uPD78F0103HMC(A1)@SSOP30 [DX1027]
uPD78F0103HMC@SSOP30 [DX1027]
uPD78F0103M1MCA@SSOP30 [DX1027]
uPD78F0103M2MC@SSOP30 [DX1027]
uPD78F0103M2MCA1@SSOP30 [DX1027]
uPD75P0076CU@SDIP42 [DX0042]
uPD75P008CU@SDIP42 [DX0042]
uPD75P108BCW@SDIP64 [DX0064]
uPD75P108BGF@PQFP64 [DX3015]
uPD75P108DW [DX0064]
uPD75P116BCW [DX0064]
uPD75P116BGF [DX3015]
uPD75P116DW [DX0064]
uPD75P218CW@PQFP64 [DX3015]
uPD75P3018AGC@TQFP80 [DX3018]
uPD75P3018GC@TQFP80 [DX3018]
uPD75P3036AGC@TQFP80 [DX3018]
uPD75P3036GC@TQFP80 [DX3018]
uPD75P308AGF@PQFP80 [DX3019]
uPD75P308BGK@PQFP80 [DX3016]
uPD75P308GF@PQFP80 [DX3019]
uPD75P316AGF@PQFP80 [DX3019]
uPD75P316BGK@PQFP80 [DX3016]
uPD75P316GF@PQFP80 [DX3019]
uPD75P54CS [DX0001]
uPD75P64CS [DX0001]
UPD76F0168AGC [DX3014]
UPD76F9108AGC [DX3014]
uPD77P20 [DX0001]
uPD78CP18CW(A) [DX0064]
uPD78CP18DW [DX0064]
uPD78CP18DW(B) [DX0064]
uPD78CP18GQ(A) [DX0065]
uPD78F0034ACW [DX0064]
uPD78F0034AGC [DX3013]
uPD78F0034AYCW [DX0064]
uPD78F0034AYGC [DX3013]
uPD78F0034BCW [DX0064]
uPD78F0034BGC [DX3013]
uPD78F0034BYCW [DX0064]
uPD78F0034BYGC [DX3013]
uPD78F0034CW [DX0064]
uPD78F0034GC [DX3013]
uPD78F0101HMC(A)@SSOP30 [DX1027]
uPD78F0102HMC(A)@SSOP30 [DX1027]
uPD78F0103HMC(A)@SSOP30 [DX1027]
uPD78F0103M1MC@SSOP30 [DX1027]
uPD78F0103M1MCA1@SSOP30 [DX1027]
uPD78F0103M2MCA@SSOP30 [DX1027]
uPD78F0103M3MC@SSOP30 [DX1027]

uPD78F0103M3MCA@SSOP30 [DX1027]
uPD78F0103M3MCA1@SSOP30 [DX1027]
uPD78F0103M4MC@SSOP30 [DX1027]
uPD78F0103M4MCA@SSOP30 [DX1027]
uPD78F0103M4MCA1@SSOP30 [DX1027]
uPD78F0103M5MC@SSOP30 [DX1027]
uPD78F0103M5MCA@SSOP30 [DX1027]
uPD78F0103M5MCA1@SSOP30 [DX1027]
uPD78F0103M6MC@SSOP30 [DX1027]
uPD78F0103M6MCA@SSOP30 [DX1027]
uPD78F0103M6MCA1@SSOP30 [DX1027]
uPD78F0103N1MC@QFP64 [DX3011]
uPD78F0103N1MCA@QFP64 [DX3011]
uPD78F0103N1MCA1@QFP64 [DX3011]
uPD78F0103N2MC@QFP64 [DX3011]
uPD78F0103N2MCA@QFP64 [DX3011]
uPD78F0103N2MCA1@QFP64 [DX3011]
uPD78F0103N3MC@QFP64 [DX3011]
uPD78F0103N3MCA@QFP64 [DX3011]
uPD78F0103N3MCA1@QFP64 [DX3011]
uPD78F0103N4MC@QFP64 [DX3011]
uPD78F0103N4MCA@QFP64 [DX3011]
uPD78F0103N4MCA1@QFP64 [DX3011]
uPD78F0103N5MC@QFP64 [DX3011]
uPD78F0103N5MCA@QFP64 [DX3011]
uPD78F0103N5MCA1@QFP64 [DX3011]
uPD78F0103N6MC@QFP64 [DX3011]
uPD78F0103N6MCA@QFP64 [DX3011]
uPD78F0103N6MCA1@QFP64 [DX3011]
uPD78F0112HGB(A)@QFP44 [DX3003]
uPD78F0112HGB(A1)@QFP44 [DX3003]
uPD78F0112HGB@QFP44 [DX3003]
uPD78F0113HGB(A)@QFP44 [DX3003]
uPD78F0113HGB(A1)@QFP44 [DX3003]
uPD78F0113HGB@QFP44 [DX3003]
uPD78F0114HDGB(A)@QFP44 [DX3003]
uPD78F0114HDGB(A1)@QFP44 [DX3003]
uPD78F0114HDGB@QFP44 [DX3003]
uPD78F0114HGB(A)@QFP44 [DX3003]
uPD78F0114HGB(A1)@QFP44 [DX3003]
uPD78F0114HGB@QFP44 [DX3003]
uPD78F0114M1GB(A)@QFP44 [DX3003]
uPD78F0114M1GB(A1)@QFP44 [DX3003]
uPD78F0114M1GB@QFP44 [DX3003]
uPD78F0114M2GB(A)@QFP44 [DX3003]
uPD78F0114M2GB(A1)@QFP44 [DX3003]
uPD78F0114M2GB@QFP44 [DX3003]
uPD78F0114M3GB(A)@QFP44 [DX3003]
uPD78F0114M3GB(A1)@QFP44 [DX3003]
uPD78F0114M3GB@QFP44 [DX3003]
uPD78F0114M4GB(A)@QFP44 [DX3003]
uPD78F0114M4GB(A1)@QFP44 [DX3003]
uPD78F0114M4GB@QFP44 [DX3003]
uPD78F0114M5GB(A)@QFP44 [DX3003]
uPD78F0114M5GB(A1)@QFP44 [DX3003]
uPD78F0114M5GB@QFP44 [DX3003]
uPD78F0114M6GB(A)@QFP44 [DX3003]
uPD78F0114M6GB(A1)@QFP44 [DX3003]
uPD78F0114M6GB@QFP44 [DX3003]
uPD78F0118M1GB(A)@QFP44 [DX3003]
uPD78F0118M1GB(A1)@QFP44 [DX3003]
uPD78F0118M1GB@QFP44 [DX3003]
uPD78F0118M2GB(A)@QFP44 [DX3003]
uPD78F0118M2GB(A1)@QFP44 [DX3003]
uPD78F0118M2GB@QFP44 [DX3003]
uPD78F0118M3GB(A)@QFP44 [DX3003]
uPD78F0118M3GB(A1)@QFP44 [DX3003]
uPD78F0118M3GB@QFP44 [DX3003]
uPD78F0118M4GB(A)@QFP44 [DX3003]
uPD78F0118M4GB(A1)@QFP44 [DX3003]
uPD78F0118M4GB@QFP44 [DX3003]
uPD78F0118M5GB(A)@QFP44 [DX3003]
uPD78F0118M5GB(A1)@QFP44 [DX3003]
uPD78F0118M5GB@QFP44 [DX3003]
uPD78F0118M6GB(A)@QFP44 [DX3003]
uPD78F0118M6GB(A1)@QFP44 [DX3003]
uPD78F0118M6GB@QFP44 [DX3003]
uPD78F0122HGB(A)@QFP52 [DX3010]
uPD78F0122HGB(A1)@QFP52 [DX3010]
uPD78F0122HGB@QFP52 [DX3010]
uPD78F0123HGB(A)@QFP52 [DX3010]
uPD78F0123HGB(A1)@QFP52 [DX3010]

uPD78F0123HGB@QFP52 [DX3010]
uPD78F0124HDGB(A)@QFP52 [DX3010]
uPD78F0124HDGB(A1)@QFP52 [DX3010]
uPD78F0124HDGB@QFP52 [DX3010]
uPD78F0124HGB(A)@QFP52 [DX3010]
uPD78F0124HGB(A1)@QFP52 [DX3010]
uPD78F0124HGB@QFP52 [DX3010]
uPD78F0132HGB(A)@QFP64 [DX3011]
uPD78F0132HGB(A1)@QFP64 [DX3011]
uPD78F0132HGB@QFP64 [DX3011]
uPD78F0132HGC(A)@QFP64 [DX3013]
uPD78F0132HGC(A1)@QFP64 [DX3013]
uPD78F0132HGC@QFP64 [DX3013]
uPD78F0132HGK(A)@QFP64 [DX3012]
uPD78F0132HGK(A1)@QFP64 [DX3012]
uPD78F0132HGK@QFP64 [DX3012]
uPD78F0133HGB(A)@QFP64 [DX3011]
uPD78F0133HGB(A1)@QFP64 [DX3011]
uPD78F0133HGB@QFP64 [DX3011]
uPD78F0133HGC(A)@QFP64 [DX3013]
uPD78F0133HGC(A1)@QFP64 [DX3013]
uPD78F0133HGC@QFP64 [DX3013]
uPD78F0133HGK(A)@QFP64 [DX3012]
uPD78F0133HGK(A1)@QFP64 [DX3012]
uPD78F0133HGK@QFP64 [DX3012]
uPD78F0134HGB(A)@QFP64 [DX3011]
uPD78F0134HGB(A1)@QFP64 [DX3011]
uPD78F0134HGB@QFP64 [DX3011]
uPD78F0134HGC(A)@QFP64 [DX3013]
uPD78F0134HGC(A1)@QFP64 [DX3013]
uPD78F0134HGC@QFP64 [DX3013]
uPD78F0134HGK(A)@QFP64 [DX3012]
uPD78F0134HGK(A1)@QFP64 [DX3012]
uPD78F0134HGK@QFP64 [DX3012]
uPD78F0134M1GB@LQFP64 [DX3011]
uPD78F0134M1GB_A@LQFP64 [DX3011]
uPD78F0134M1GBA@LQFP64 [DX3011]
uPD78F0134M1GBA1@LQFP64 [DX3011]
uPD78F0134M1GC@LQFP64 [DX3013]
uPD78F0134M1GC_A@LQFP64 [DX3013]
uPD78F0134M1GCA@LQFP64 [DX3013]
uPD78F0134M1GCA1@LQFP64 [DX3013]
uPD78F0134M1GK@TQFP64 [DX3012]
uPD78F0134M1GK_A@TQFP64 [DX3012]
uPD78F0134M1GKA@TQFP64 [DX3012]
uPD78F0134M1GKA1@TQFP64 [DX3012]
uPD78F0134M2GB@LQFP64 [DX3011]
uPD78F0134M2GB_A@LQFP64 [DX3011]
uPD78F0134M2GBA1@LQFP64 [DX3011]
uPD78F0134M2GC@LQFP64 [DX3013]
uPD78F0134M2GC_A@LQFP64 [DX3013]
uPD78F0134M2GCA@LQFP64 [DX3013]
uPD78F0134M2GCA1@LQFP64 [DX3013]
uPD78F0134M2GK@TQFP64 [DX3012]
uPD78F0134M2GK_A@TQFP64 [DX3012]
uPD78F0134M2GKA@TQFP64 [DX3012]
uPD78F0134M2GKA1@TQFP64 [DX3012]
uPD78F0134M3GB@LQFP64 [DX3011]
uPD78F0134M3GB_A@LQFP64 [DX3011]
uPD78F0134M3GBA@LQFP64 [DX3011]
uPD78F0134M3GBA1@LQFP64 [DX3011]
uPD78F0134M3GC@LQFP64 [DX3013]
uPD78F0134M3GC_A@LQFP64 [DX3013]
uPD78F0134M3GCA@LQFP64 [DX3013]
uPD78F0134M3GCA1@LQFP64 [DX3013]
uPD78F0134M3GK@TQFP64 [DX3012]
uPD78F0134M3GK_A@TQFP64 [DX3012]
uPD78F0134M3GKA@TQFP64 [DX3012]
uPD78F0134M3GKA1@TQFP64 [DX3012]
uPD78F0134M4GB@LQFP64 [DX3011]
uPD78F0134M4GB_A@LQFP64 [DX3011]
uPD78F0134M4GBA@LQFP64 [DX3011]
uPD78F0134M4GBA1@LQFP64 [DX3011]
uPD78F0134M4GC@LQFP64 [DX3013]
uPD78F0134M4GC_A@LQFP64 [DX3013]
uPD78F0134M4GCA@LQFP64 [DX3013]
uPD78F0134M4GCA1@LQFP64 [DX3013]
uPD78F0134M4GK@TQFP64 [DX3012]
uPD78F0134M4GK_A@TQFP64 [DX3012]
uPD78F0134M4GKA@TQFP64 [DX3012]
uPD78F0134M4GKA1@TQFP64 [DX3012]
uPD78F0134M5GB@LQFP64 [DX3011]
uPD78F0134M5GB_A@LQFP64 [DX3011]
uPD78F0134M5GBA@LQFP64 [DX3011]
uPD78F0134M5GBA1@LQFP64 [DX3011]
uPD78F0134M5GC@LQFP64 [DX3013]
uPD78F0134M5GC_A@LQFP64 [DX3013]
uPD78F0134M5GCA@LQFP64 [DX3013]
uPD78F0134M5GCA1@LQFP64 [DX3013]
uPD78F0134M5GK@TQFP64 [DX3012]
uPD78F0134M5GK_A@TQFP64 [DX3012]
uPD78F0134M5GKA@TQFP64 [DX3012]
uPD78F0134M5GKA1@TQFP64 [DX3012]
uPD78F0134M6GB@LQFP64 [DX3011]
uPD78F0134M6GB_A@LQFP64 [DX3011]

uPD78F0134M6GBA@LQFP64 [DX3011]
uPD78F0134M6GBA1@LQFP64 [DX3011]
uPD78F0134M6GC@LQFP64 [DX3013]
uPD78F0134M6GC_A@LQFP64 [DX3013]
uPD78F0134M6GCA@LQFP64 [DX3013]
uPD78F0134M6GCA1@LQFP64 [DX3013]
uPD78F0134M6GK@TQFP64 [DX3012]
uPD78F0134M6GK_A@TQFP64 [DX3012]
uPD78F0134M6GKA@TQFP64 [DX3012]
uPD78F0134M6GKA1@TQFP64 [DX3012]
uPD78F0136HGB(A)@QFP64 [DX3011]
uPD78F0136HGB(A1)@QFP64 [DX3011]
uPD78F0136HGB@QFP64 [DX3011]
uPD78F0136HGC(A)@QFP64 [DX3013]
uPD78F0136HGC(A1)@QFP64 [DX3013]
uPD78F0136HGC@QFP64 [DX3013]
uPD78F0136HGK(A)@QFP64 [DX3012]
uPD78F0136HGK(A1)@QFP64 [DX3012]
uPD78F0136HGK@QFP64 [DX3012]
uPD78F0138HDGB(A)@QFP64 [DX3011]
uPD78F0138HDGB(A1)@QFP64 [DX3011]
uPD78F0138HDGB@QFP64 [DX3011]
uPD78F0138HDGC(A)@QFP64 [DX3013]
uPD78F0138HDGC(A1)@QFP64 [DX3013]
uPD78F0138HDGC@QFP64 [DX3013]
uPD78F0138HDGK(A)@QFP64 [DX3012]
uPD78F0138HDGK(A1)@QFP64 [DX3012]
uPD78F0138HDGK@QFP64 [DX3012]
uPD78F0138HGB(A)@QFP64 [DX3011]
uPD78F0138HGB(A1)@QFP64 [DX3011]
uPD78F0138HGB@QFP64 [DX3011]
uPD78F0138HGC(A)@QFP64 [DX3013]
uPD78F0138HGC(A1)@QFP64 [DX3013]
uPD78F0138HGC@QFP64 [DX3013]
uPD78F0138HGK(A)@QFP64 [DX3012]
uPD78F0138HGK(A1)@QFP64 [DX3012]
uPD78F0138HGK@QFP64 [DX3012]
uPD78F0138M1GB@LQFP64 [DX3011]
uPD78F0138M1GB_A@LQFP64 [DX3011]
uPD78F0138M1GBA@LQFP64 [DX3011]
uPD78F0138M1GBA1@LQFP64 [DX3011]
uPD78F0138M1GC@LQFP64 [DX3013]
uPD78F0138M1GC_A@LQFP64 [DX3013]
uPD78F0138M1GCA@LQFP64 [DX3013]
uPD78F0138M1GCA1@LQFP64 [DX3013]
uPD78F0138M1GK@TQFP64 [DX3012]
uPD78F0138M1GK_A@TQFP64 [DX3012]
uPD78F0138M1GKA@TQFP64 [DX3012]
uPD78F0138M1GKA1@TQFP64 [DX3012]
uPD78F0138M2GB@LQFP64 [DX3011]
uPD78F0138M2GB_A@LQFP64 [DX3011]
uPD78F0138M2GBA@LQFP64 [DX3011]
uPD78F0138M2GBA1@LQFP64 [DX3011]
uPD78F0138M2GC@LQFP64 [DX3013]
uPD78F0138M2GC_A@LQFP64 [DX3013]
uPD78F0138M2GCA@LQFP64 [DX3013]
uPD78F0138M2GCA1@LQFP64 [DX3013]
uPD78F0138M2GK@TQFP64 [DX3012]
uPD78F0138M2GK_A@TQFP64 [DX3012]
uPD78F0138M2GKA@TQFP64 [DX3012]
uPD78F0138M2GKA1@TQFP64 [DX3012]
uPD78F0138M3GB@LQFP64 [DX3011]
uPD78F0138M3GB_A@LQFP64 [DX3011]
uPD78F0138M3GBA@LQFP64 [DX3011]
uPD78F0138M3GBA1@LQFP64 [DX3011]
uPD78F0138M3GC@LQFP64 [DX3013]
uPD78F0138M3GC_A@LQFP64 [DX3013]
uPD78F0138M3GCA@LQFP64 [DX3013]
uPD78F0138M3GCA1@LQFP64 [DX3013]
uPD78F0138M3GK@TQFP64 [DX3012]
uPD78F0138M3GK_A@TQFP64 [DX3012]
uPD78F0138M3GKA@TQFP64 [DX3012]
uPD78F0138M3GKA1@TQFP64 [DX3012]
uPD78F0138M4GB@LQFP64 [DX3011]
uPD78F0138M4GB_A@LQFP64 [DX3011]
uPD78F0138M4GBA@LQFP64 [DX3011]
uPD78F0138M4GBA1@LQFP64 [DX3011]
uPD78F0138M4GC@LQFP64 [DX3013]
uPD78F0138M4GC_A@LQFP64 [DX3013]
uPD78F0138M4GCA@LQFP64 [DX3013]
uPD78F0138M4GCA1@LQFP64 [DX3013]
uPD78F0138M4GK@TQFP64 [DX3012]
uPD78F0138M4GK_A@TQFP64 [DX3012]
uPD78F0138M4GKA@TQFP64 [DX3012]
uPD78F0138M4GKA1@TQFP64 [DX3012]
uPD78F0138M5GB@LQFP64 [DX3011]
uPD78F0138M5GB_A@LQFP64 [DX3011]
uPD78F0138M5GBA@LQFP64 [DX3011]
uPD78F0138M5GBA1@LQFP64 [DX3011]
uPD78F0138M5GC@LQFP64 [DX3013]
uPD78F0138M5GC_A@LQFP64 [DX3013]
uPD78F0138M5GCA@LQFP64 [DX3013]
uPD78F0138M5GCA1@LQFP64 [DX3013]

uPD78F0138M5GK@TQFP64 [DX3012]
uPD78F0138M5GK_A@TQFP64 [DX3012]
uPD78F0138M5GKA@TQFP64 [DX3012]
uPD78F0138M5GKA1@TQFP64 [DX3012]
uPD78F0138M6GB@LQFP64 [DX3011]
uPD78F0138M6GB_A@LQFP64 [DX3011]
uPD78F0138M6GBA@LQFP64 [DX3011]
uPD78F0138M6GBA1@LQFP64 [DX3011]
uPD78F0138M6GC@LQFP64 [DX3013]
uPD78F0138M6GC_A@LQFP64 [DX3013]
uPD78F0138M6GCA@LQFP64 [DX3013]
uPD78F0138M6GCA1@LQFP64 [DX3013]
uPD78F0138M6GK@TQFP64 [DX3012]
uPD78F0138M6GK_A@TQFP64 [DX3012]
uPD78F0138M6GKA@TQFP64 [DX3012]
uPD78F0138M6GKA1@TQFP64 [DX3012]
uPD78F013M2GBA@LQFP64 [DX3011]
uPD78F0148M1GC(A)@QFP80 [DX3018]
uPD78F0148M1GC(A1)@QFP80 [DX3018]
uPD78F0148M1GC@QFP80 [DX3018]
uPD78F0148M1GK(A)@QFP80 [DX3016]
uPD78F0148M1GK(A1)@QFP80 [DX3016]
uPD78F0148M1GK@QFP80 [DX3016]
uPD78F0148M2GC(A)@QFP80 [DX3018]
uPD78F0148M2GC(A1)@QFP80 [DX3018]
uPD78F0148M2GC@QFP80 [DX3018]
uPD78F0148M2GK(A)@QFP80 [DX3016]
uPD78F0148M2GK(A1)@QFP80 [DX3016]
uPD78F0148M2GK@QFP80 [DX3016]
uPD78F0148M3GC(A)@QFP80 [DX3018]
uPD78F0148M3GC(A1)@QFP80 [DX3018]
uPD78F0148M3GC@QFP80 [DX3018]
uPD78F0148M3GK(A)@QFP80 [DX3016]
uPD78F0148M3GK(A1)@QFP80 [DX3016]
uPD78F0148M3GK@QFP80 [DX3016]
uPD78F0148M4GC(A)@QFP80 [DX3018]
uPD78F0148M4GC(A1)@QFP80 [DX3018]
uPD78F0148M4GC@QFP80 [DX3018]
uPD78F0148M4GK(A)@QFP80 [DX3016]
uPD78F0148M4GK(A1)@QFP80 [DX3016]
uPD78F0148M4GK@QFP80 [DX3016]
uPD78F0148M5GC(A)@QFP80 [DX3018]
uPD78F0148M5GC(A1)@QFP80 [DX3018]
uPD78F0148M5GC@QFP80 [DX3018]
uPD78F0148M5GK(A)@QFP80 [DX3016]
uPD78F0148M5GK(A1)@QFP80 [DX3016]
uPD78F0148M5GK@QFP80 [DX3016]
uPD78F0148M6GC(A)@QFP80 [DX3018]
uPD78F0148M6GC(A1)@QFP80 [DX3018]
uPD78F0148M6GC@QFP80 [DX3018]
uPD78F0148M6GK(A)@QFP80 [DX3016]
uPD78F0148M6GK(A1)@QFP80 [DX3016]
uPD78F0148M6GK@QFP80 [DX3016]
uPD78F0361AGB [DX3011]
uPD78F0361AGK [DX3012]
uPD78F0361GB [DX3011]
uPD78F0361GK [DX3012]
uPD78F0362AGB [DX3011]
uPD78F0362AGK [DX3012]
uPD78F0362GB [DX3011]
uPD78F0362GK [DX3012]
uPD78F0363ADGB [DX3011]
uPD78F0363ADGK [DX3012]
uPD78F0363AGB [DX3011]
uPD78F0363AGK [DX3012]
uPD78F0363DGB [DX3011]
uPD78F0363DGK [DX3012]
uPD78F0363GB [DX3011]
uPD78F0363GK [DX3012]
uPD78F0364AGB [DX3011]
uPD78F0364AGK [DX3012]
uPD78F0364GB [DX3011]
uPD78F0364GK [DX3012]
uPD78F0365AGB [DX3011]
uPD78F0365AGK [DX3012]
uPD78F0365GB [DX3011]
uPD78F0365GK [DX3012]
uPD78F0366AGB [DX3011]
uPD78F0366AGK [DX3012]
uPD78F0366GB [DX3011]
uPD78F0366GK [DX3012]
uPD78F0367ADGB [DX3011]
uPD78F0367ADGK [DX3012]
uPD78F0367AGB [DX3011]

uPD78F0367AGK [DX3012]
uPD78F0367DGK [DX3012]
uPD78F0367GK [DX3012]
uPD78F0371AGK [DX3016]
uPD78F0371GK [DX3016]
uPD78F0372AGK [DX3016]
uPD78F0372GK [DX3016]
uPD78F0373ADGK [DX3016]
uPD78F0373AGK [DX3016]
uPD78F0373DGK [DX3016]
uPD78F0373GK [DX3016]
uPD78F0374AGK [DX3016]
uPD78F0374GK [DX3016]
uPD78F0375AGK [DX3016]
uPD78F0375GK [DX3016]
uPD78F0376ADGK [DX3016]
uPD78F0376AGK [DX3016]
uPD78F0376DGK [DX3016]
uPD78F0376GK [DX3016]
uPD78F0377ADGK [DX3016]
uPD78F0377AGK [DX3016]
uPD78F0377DGK [DX3016]
uPD78F0377GK [DX3016]
uPD78F0381AGK [DX3016]
uPD78F0381GK [DX3016]
uPD78F0382AGK [DX3016]
uPD78F0382GK [DX3016]
uPD78F0383ADGK [DX3016]
uPD78F0383AGK [DX3016]
uPD78F0383DGK [DX3016]
uPD78F0383GK [DX3016]
uPD78F0384AGK [DX3016]
uPD78F0384GK [DX3016]
uPD78F0385AGK [DX3016]
uPD78F0385GK [DX3016]
uPD78F0386ADGK [DX3016]
uPD78F0386AGK [DX3016]
uPD78F0386DGK [DX3016]
uPD78F0386GK [DX3016]
uPD78F0387ADGK [DX3016]
uPD78F0387AGK [DX3016]
uPD78F0387DGK [DX3016]
uPD78F0387GK [DX3016]
uPD78F0391GC [DX3043]
uPD78F0392GC [DX3043]
uPD78F0393AGC [DX3043]
uPD78F0393GC [DX3043]
uPD78F0394GC [DX3043]
uPD78F0367DGB [DX3011]
uPD78F0367GB [DX3011]
uPD78F0371AGC [DX3017]
uPD78F0371GC [DX3017]
uPD78F0372AGC [DX3017]
uPD78F0372GC [DX3017]
uPD78F0373ADGC [DX3017]
uPD78F0373AGC [DX3017]
uPD78F0373DGC [DX3017]
uPD78F0373GC [DX3017]
uPD78F0374AGC [DX3017]
uPD78F0374GC [DX3017]
uPD78F0375AGC [DX3017]
uPD78F0375GC [DX3017]
uPD78F0376ADGC [DX3017]
uPD78F0376AGC [DX3017]
uPD78F0376DGC [DX3017]
uPD78F0376GC [DX3017]
uPD78F0377ADGC [DX3017]
uPD78F0377AGC [DX3017]
uPD78F0377DGC [DX3017]
uPD78F0377GC [DX3017]
uPD78F0381AGC [DX3017]
uPD78F0381GC [DX3017]
uPD78F0382AGC [DX3017]
uPD78F0382GC [DX3017]
uPD78F0383ADGC [DX3017]
uPD78F0383AGC [DX3017]
uPD78F0383DGC [DX3017]
uPD78F0383GC [DX3017]
uPD78F0384AGC [DX3017]
uPD78F0384GC [DX3017]
uPD78F0385AGC [DX3017]
uPD78F0385GC [DX3017]
uPD78F0386ADGC [DX3017]
uPD78F0386AGC [DX3017]
uPD78F0386DGC [DX3017]
uPD78F0386GC [DX3017]
uPD78F0387ADGC [DX3017]
uPD78F0387AGC [DX3017]
uPD78F0387DGC [DX3017]
uPD78F0387GC [DX3017]
uPD78F0391AGC [DX3043]
uPD78F0392AGC [DX3043]
uPD78F0393ADGC [DX3043]
uPD78F0393DGC [DX3043]
uPD78F0394AGC [DX3043]
uPD78F0395AGC [DX3043]

uPD78F0395GC [DX3043]
uPD78F0396AGC [DX3043]
uPD78F0396GC [DX3043]
uPD78F0397AGC [DX3043]
uPD78F0397GC [DX3043]
uPD78F0401GA@LQFP48 [DX3047]
uPD78F0403GA@LQFP48 [DX3047]
uPD78F0405GA@LQFP48 [DX3047]
uPD78F0411GA@LQFP48 [DX3047]
uPD78F0413GA@LQFP48 [DX3047]
uPD78F0415GA@LQFP48 [DX3047]
uPD78F0421GB@LQFP52 [DX3010]
uPD78F0423GB@LQFP52 [DX3010]
uPD78F0425GB@LQFP52 [DX3010]
uPD78F0431GB@LQFP52 [DX3010]
uPD78F0433GB@LQFP52 [DX3010]
uPD78F0435GB@LQFP52 [DX3010]
uPD78F0440GK@LQFP64 [DX3012]
uPD78F0441GK@LQFP64 [DX3012]
uPD78F0442GK@LQFP64 [DX3012]
uPD78F0443GK@LQFP64 [DX3012]
uPD78F0444GK@LQFP64 [DX3012]
uPD78F0445GK@LQFP64 [DX3012]
uPD78F0450GK@LQFP64 [DX3012]
uPD78F0451GK@LQFP64 [DX3012]
uPD78F0452GK@LQFP64 [DX3012]
uPD78F0453GK@LQFP64 [DX3012]
uPD78F0454GK@LQFP64 [DX3012]
uPD78F0455GK@LQFP64 [DX3012]
uPD78F0460GK@LQFP64 [DX3012]
uPD78F0461GK@LQFP64 [DX3012]
uPD78F0462GK@LQFP64 [DX3012]
uPD78F0463GK@LQFP64 [DX3012]
uPD78F0464GK@LQFP64 [DX3012]
uPD78F0465GK@LQFP64 [DX3012]
uPD78F0470GK@LQFP80 [DX3016]
uPD78F0471GK@LQFP80 [DX3016]
uPD78F0472GK@LQFP80 [DX3016]
uPD78F0473GK@LQFP80 [DX3016]
uPD78F0474GK@LQFP80 [DX3016]
uPD78F0475GK@LQFP80 [DX3016]
uPD78F0480GK@LQFP80 [DX3016]
uPD78F0481GK@LQFP80 [DX3016]
uPD78F0482GK@LQFP80 [DX3016]
uPD78F0483GK@LQFP80 [DX3016]
uPD78F0484GK@LQFP80 [DX3016]
uPD78F0485GK@LQFP80 [DX3016]
uPD78F0490GK@LQFP80 [DX3016]
uPD78F0396ADGC [DX3043]
uPD78F0396DGC [DX3043]
uPD78F0397ADGC [DX3043]
uPD78F0397DGC [DX3043]
uPD78F0400GA@LQFP48 [DX3047]
uPD78F0402GA@LQFP48 [DX3047]
uPD78F0404GA@LQFP48 [DX3047]
uPD78F0410GA@LQFP48 [DX3047]
uPD78F0412GA@LQFP48 [DX3047]
uPD78F0414GA@LQFP48 [DX3047]
uPD78F0420GB@LQFP52 [DX3010]
uPD78F0422GB@LQFP52 [DX3010]
uPD78F0424GB@LQFP52 [DX3010]
uPD78F0430GB@LQFP52 [DX3010]
uPD78F0432GB@LQFP52 [DX3010]
uPD78F0434GB@LQFP52 [DX3010]
uPD78F0440GB@LQFP64 [DX3011]
uPD78F0441GB@LQFP64 [DX3011]
uPD78F0442GB@LQFP64 [DX3011]
uPD78F0443GB@LQFP64 [DX3011]
uPD78F0444GB@LQFP64 [DX3011]
uPD78F0445GB@LQFP64 [DX3011]
uPD78F0450GB@LQFP64 [DX3011]
uPD78F0451GB@LQFP64 [DX3011]
uPD78F0452GB@LQFP64 [DX3011]
uPD78F0453GB@LQFP64 [DX3011]
uPD78F0454GB@LQFP64 [DX3011]
uPD78F0455GB@LQFP64 [DX3011]
uPD78F0460GB@LQFP64 [DX3011]
uPD78F0461GB@LQFP64 [DX3011]
uPD78F0462GB@LQFP64 [DX3011]
uPD78F0463GB@LQFP64 [DX3011]
uPD78F0464GB@LQFP64 [DX3011]
uPD78F0465GB@LQFP64 [DX3011]
uPD78F0470GC@LQFP80 [DX3017]
uPD78F0471GC@LQFP80 [DX3017]
uPD78F0472GC@LQFP80 [DX3017]
uPD78F0473GC@LQFP80 [DX3017]
uPD78F0474GC@LQFP80 [DX3017]
uPD78F0475GC@LQFP80 [DX3017]
uPD78F0480GC@LQFP80 [DX3017]
uPD78F0481GC@LQFP80 [DX3017]
uPD78F0482GC@LQFP80 [DX3017]
uPD78F0483GC@LQFP80 [DX3017]
uPD78F0484GC@LQFP80 [DX3017]
uPD78F0485GC@LQFP80 [DX3017]
uPD78F0490GC@LQFP80 [DX3017]
uPD78F0491GC@LQFP80 [DX3017]

uPD78F0491GK@LQFP80 [DX3016]
uPD78F0492GC@LQFP80 [DX3017]
uPD78F0492GK@LQFP80 [DX3016]
uPD78F0493GC@LQFP80 [DX3017]
uPD78F0493GK@LQFP80 [DX3016]
uPD78F0494GC@LQFP80 [DX3017]
uPD78F0494GK@LQFP80 [DX3016]
uPD78F0495GC@LQFP80 [DX3017]
uPD78F0495GK@LQFP80 [DX3016]
uPD78F0500AAQS [DX1087]
uPD78F0500AAQSA [DX1087]
uPD78F0500AFC@FLGA36
uPD78F0500AMC(A)@SSOP30 [DX1087]
uPD78F0500AMC@SSOP30 [DX1087]
uPD78F0500AQS [DX1087]
uPD78F0500AQSA [DX1087]
uPD78F0500FC@FLGA36
uPD78F0500MC(A)@SSOP30 [DX1087]
uPD78F0500MC@SSOP30 [DX1087]
uPD78F0501AAQS [DX1087]
uPD78F0501AAQSA [DX1087]
uPD78F0501AFC@FLGA36
uPD78F0501AMC(A)@SSOP30 [DX1087]
uPD78F0501AMC@SSOP30 [DX1087]
uPD78F0501AQS [DX1087]
uPD78F0501AQSA [DX1087]
uPD78F0501FC@FLGA36
uPD78F0501MC(A)@SSOP30 [DX1087]
uPD78F0501MC@SSOP30 [DX1087]
uPD78F0502AAQS [DX1087]
uPD78F0502AAQSA [DX1087]
uPD78F0502AFC@FLGA36
uPD78F0502AMC(A)@SSOP30 [DX1087]
uPD78F0502AMC@SSOP30 [DX1087]
uPD78F0502AQS [DX1087]
uPD78F0502AQSA [DX1087]
uPD78F0502FC@FLGA36
uPD78F0502MC(A)@SSOP30 [DX1087]
uPD78F0502MC@SSOP30 [DX1087]
uPD78F0503AAQS [DX1087]
uPD78F0503AAQSA [DX1087]
uPD78F0503ADFC@FLGA36
uPD78F0503ADMC(A)@SSOP30 [DX1087]
uPD78F0503ADMC@SSOP30 [DX1087]
uPD78F0503AFC@FLGA36
uPD78F0503AMC(A)@SSOP30 [DX1087]
uPD78F0503AMC@SSOP30 [DX1087]
uPD78F0503AQS [DX1087]
uPD78F0503AQSA [DX1087]
uPD78F0503DFC@FLGA36
uPD78F0503DMC(A)@SSOP30 [DX1087]
uPD78F0503DMC@SSOP30 [DX1087]
uPD78F0503FC@FLGA36
uPD78F0503MC(A)@SSOP30 [DX1087]
uPD78F0503MC@SSOP30 [DX1087]
uPD78F0511AGA(A)@TQFP48 [DX3047]
uPD78F0511AGA(A2)@TQFP48 [DX3047]
uPD78F0511AGA@TQFP48 [DX3047]
uPD78F0511AGB(A)@TQFP44 [DX3005]
uPD78F0511AGB(A2)@TQFP44 [DX3005]
uPD78F0511AGB@TQFP44 [DX3005]
uPD78F0511AMC@SSOP38 [DX1087]
uPD78F0511GA(A)@TQFP48 [DX3047]
uPD78F0511GA(A2)@TQFP48 [DX3047]
uPD78F0511GA@TQFP48 [DX3047]
uPD78F0511GB(A)@TQFP44 [DX3005]
uPD78F0511GB(A2)@TQFP44 [DX3005]
uPD78F0511GB@TQFP44 [DX3005]
uPD78F0511MC@SSOP38 [DX1087]
uPD78F0512AGA(A)@TQFP48 [DX3047]
uPD78F0512AGA(A2)@TQFP48 [DX3047]
uPD78F0512AGA@TQFP48 [DX3047]
uPD78F0512AGB(A)@TQFP44 [DX3005]
uPD78F0512AGB(A2)@TQFP44 [DX3005]
uPD78F0512AGB@TQFP44 [DX3005]
uPD78F0512AMC@SSOP38 [DX1087]
uPD78F0512GA(A)@TQFP48 [DX3047]
uPD78F0512GA(A2)@TQFP48 [DX3047]
uPD78F0512GA@TQFP48 [DX3047]
uPD78F0512GB(A)@TQFP44 [DX3005]
uPD78F0512GB(A2)@TQFP44 [DX3005]
uPD78F0512GB@TQFP44 [DX3005]
uPD78F0512MC@SSOP38 [DX1087]
uPD78F0513ADGA(A)@TQFP48 [DX3047]
uPD78F0513ADGA(A2)@TQFP48 [DX3047]
uPD78F0513ADGA@TQFP48 [DX3047]

uPD78F0513ADGB(A)@TQFP44 [DX3005]
uPD78F0513ADGB(A2)@TQFP44 [DX3005]
uPD78F0513ADGB@TQFP44 [DX3005]
uPD78F0513ADMC@SSOP38 [DX1087]
uPD78F0513AGA(A)@TQFP48 [DX3047]
uPD78F0513AGA(A2)@TQFP48 [DX3047]
uPD78F0513AGA@TQFP48 [DX3047]
uPD78F0513AGB(A)@TQFP44 [DX3005]
uPD78F0513AGB(A2)@TQFP44 [DX3005]
uPD78F0513AGB@TQFP44 [DX3005]
uPD78F0513AMC@SSOP38 [DX1087]
uPD78F0513DGA(A)@TQFP48 [DX3047]
uPD78F0513DGA(A2)@TQFP48 [DX3047]
uPD78F0513DGA@TQFP48 [DX3047]
uPD78F0513DGB(A)@TQFP44 [DX3005]
uPD78F0513DGB(A2)@TQFP44 [DX3005]
uPD78F0513DGB@TQFP44 [DX3005]
uPD78F0513DMC@SSOP38 [DX1087]
uPD78F0513GA(A)@TQFP48 [DX3047]
uPD78F0513GA(A2)@TQFP48 [DX3047]
uPD78F0513GA@TQFP48 [DX3047]
uPD78F0513GB(A)@TQFP44 [DX3005]
uPD78F0513GB(A2)@TQFP44 [DX3005]
uPD78F0513GB@TQFP44 [DX3005]
uPD78F0513MC@SSOP38 [DX1087]
uPD78F0514AGA(A)@TQFP48 [DX3047]
uPD78F0514AGA(A2)@TQFP48 [DX3047]
uPD78F0514AGA@TQFP48 [DX3047]
uPD78F0514AGB(A)@TQFP44 [DX3005]
uPD78F0514AGB(A2)@TQFP44 [DX3005]
uPD78F0514AGB@TQFP44 [DX3005]
uPD78F0514AMC@SSOP38 [DX1087]
uPD78F0514GA(A)@TQFP48 [DX3047]
uPD78F0514GA(A2)@TQFP48 [DX3047]
uPD78F0514GA@TQFP48 [DX3047]
uPD78F0514GB(A)@TQFP44 [DX3005]
uPD78F0514GB(A2)@TQFP44 [DX3005]
uPD78F0514GB@TQFP44 [DX3005]
uPD78F0514MC@SSOP38 [DX1087]
uPD78F0515AGA(A)@TQFP48 [DX3047]
uPD78F0515AGA(A2)@TQFP48 [DX3047]
uPD78F0515AGA@TQFP48 [DX3047]
uPD78F0515AGB(A)@TQFP44 [DX3005]
uPD78F0515AGB(A2)@TQFP44 [DX3005]
uPD78F0515AGB@TQFP44 [DX3005]
uPD78F0515AMC@SSOP38 [DX1087]
uPD78F0515GA(A)@TQFP48 [DX3047]
uPD78F0515GA(A2)@TQFP48 [DX3047]
uPD78F0515GA@TQFP48 [DX3047]
uPD78F0515GB(A)@TQFP44 [DX3005]
uPD78F0515GB(A2)@TQFP44 [DX3005]
uPD78F0515GB@TQFP44 [DX3005]
uPD78F0515MC@SSOP38 [DX1087]
uPD78F0521AGB(A)@LQFP52 [DX3010]
uPD78F0521AGB(A2)@LQFP52 [DX3010]
uPD78F0521AGB@LQFP52 [DX3010]
uPD78F0521GB(A)@LQFP52 [DX3010]
uPD78F0521GB(A)@LQFP52(Uart) [DX3010]
uPD78F0521GB(A2)@LQFP52 [DX3010]
uPD78F0521GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0521GB@LQFP52 [DX3010]
uPD78F0521GB@LQFP52(Uart) [DX3010]
uPD78F0522AGB(A)@LQFP52 [DX3010]
uPD78F0522AGB(A2)@LQFP52 [DX3010]
uPD78F0522AGB@LQFP52 [DX3010]
uPD78F0522GB(A)@LQFP52 [DX3010]
uPD78F0522GB(A)@LQFP52(Uart) [DX3010]
uPD78F0522GB(A2)@LQFP52 [DX3010]
uPD78F0522GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0522GB@LQFP52 [DX3010]
uPD78F0522GB@LQFP52(Uart) [DX3010]

uPD78F0523ADGB(A)@LQFP52 [DX3010]
uPD78F0523ADGB(A2)@LQFP52 [DX3010]
uPD78F0523ADGB@LQFP52 [DX3010]
uPD78F0523AGB(A)@LQFP52 [DX3010]
uPD78F0523AGB(A2)@LQFP52 [DX3010]
uPD78F0523AGB@LQFP52 [DX3010]
uPD78F0523DGB(A)@LQFP52 [DX3010]
uPD78F0523DGB(A)@LQFP52(Uart) [DX3010]
uPD78F0523DGB(A2)@LQFP52 [DX3010]
uPD78F0523DGB(A2)@LQFP52(Uart) [DX3010]
uPD78F0523DGB@LQFP52 [DX3010]
uPD78F0523DGB@LQFP52(Uart) [DX3010]
uPD78F0523GB(A)@LQFP52 [DX3010]
uPD78F0523GB(A)@LQFP52(Uart) [DX3010]
uPD78F0523GB(A2)@LQFP52 [DX3010]
uPD78F0523GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0523GB@LQFP52 [DX3010]
uPD78F0523GB@LQFP52(Uart) [DX3010]
uPD78F0524AGB(A)@LQFP52 [DX3010]
uPD78F0524AGB(A2)@LQFP52 [DX3010]
uPD78F0524AGB@LQFP52 [DX3010]
uPD78F0524GB(A)@LQFP52 [DX3010]
uPD78F0524GB(A)@LQFP52(Uart) [DX3010]
uPD78F0524GB(A2)@LQFP52 [DX3010]
uPD78F0524GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0524GB@LQFP52 [DX3010]
uPD78F0524GB@LQFP52(Uart) [DX3010]
uPD78F0525AGB(A)@LQFP52 [DX3010]
uPD78F0525AGB(A2)@LQFP52 [DX3010]
uPD78F0525AGB@LQFP52 [DX3010]
uPD78F0525GB(A)@LQFP52 [DX3010]
uPD78F0525GB(A)@LQFP52(Uart) [DX3010]
uPD78F0525GB(A2)@LQFP52 [DX3010]
uPD78F0525GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0525GB@LQFP52 [DX3010]
uPD78F0525GB@LQFP52(Uart) [DX3010]
uPD78F0526AGB(A)@LQFP52 [DX3010]
uPD78F0526AGB(A2)@LQFP52 [DX3010]
uPD78F0526AGB@LQFP52 [DX3010]
uPD78F0526GB(A)@LQFP52 [DX3010]
uPD78F0526GB(A)@LQFP52(Uart) [DX3010]
uPD78F0526GB(A2)@LQFP52 [DX3010]
uPD78F0526GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0526GB@LQFP52 [DX3010]
uPD78F0526GB@LQFP52(Uart) [DX3010]
uPD78F0527AGB(A)@LQFP52 [DX3010]
uPD78F0527AGB(A2)@LQFP52 [DX3010]
uPD78F0527AGB@LQFP52 [DX3010]
uPD78F0527GB(A)@LQFP52 [DX3010]
uPD78F0527GB(A)@LQFP52(Uart) [DX3010]
uPD78F0527GB(A2)@LQFP52 [DX3010]
uPD78F0527GB(A2)@LQFP52(Uart) [DX3010]
uPD78F0527GB@LQFP52 [DX3010]
uPD78F0527GB@LQFP52(Uart) [DX3010]

uPD78F0531AGB(A)@LQFP64 [DX3011]
uPD78F0531AGB(A2)@LQFP64 [DX3011]
uPD78F0531AGB@LQFP64 [DX3011]
uPD78F0531AGC(A)@LQFP64 [DX3013]
uPD78F0531AGC(A2)@LQFP64 [DX3013]
uPD78F0531AGC@LQFP64 [DX3013]
uPD78F0531AGK(A)@LQFP64 [DX3012]
uPD78F0531AGK(A2)@LQFP64 [DX3012]
uPD78F0531AGK@LQFP64 [DX3012]
uPD78F0531GA [DX3085]
uPD78F0531GB(A)@LQFP64 [DX3011]
uPD78F0531GB(A2)@LQFP64 [DX3011]
uPD78F0531GB@LQFP64 [DX3011]
uPD78F0531GC(A)@LQFP64 [DX3013]
uPD78F0531GC(A2)@LQFP64 [DX3013]
uPD78F0531GC@LQFP64 [DX3013]
uPD78F0531GK(A)@LQFP64 [DX3012]
uPD78F0531GK(A2)@LQFP64 [DX3012]
uPD78F0531GK@LQFP64 [DX3012]
uPD78F0532AGB(A)@LQFP64 [DX3011]
uPD78F0532AGB(A2)@LQFP64 [DX3011]
uPD78F0532AGB@LQFP64 [DX3011]
uPD78F0532AGC(A)@LQFP64 [DX3013]
uPD78F0532AGC(A2)@LQFP64 [DX3013]
uPD78F0532AGC@LQFP64 [DX3013]
uPD78F0532AGK(A)@LQFP64 [DX3012]
uPD78F0532AGK(A2)@LQFP64 [DX3012]
uPD78F0532AGK@LQFP64 [DX3012]
uPD78F0532GA [DX3085]
uPD78F0532GB(A)@LQFP64 [DX3011]
uPD78F0532GB(A2)@LQFP64 [DX3011]
uPD78F0532GB@LQFP64 [DX3011]
uPD78F0532GC(A)@LQFP64 [DX3013]
uPD78F0532GC(A2)@LQFP64 [DX3013]
uPD78F0532GC@LQFP64 [DX3013]
uPD78F0532GK(A)@LQFP64 [DX3012]
uPD78F0532GK(A2)@LQFP64 [DX3012]
uPD78F0532GK@LQFP64 [DX3012]
uPD78F0533ADGB(A)@LQFP64 [DX3011]
uPD78F0533ADGB(A2)@LQFP64 [DX3011]
uPD78F0533ADGB@LQFP64 [DX3011]
uPD78F0533ADGC(A)@LQFP64 [DX3013]
uPD78F0533ADGC(A2)@LQFP64 [DX3013]
uPD78F0533ADGC@LQFP64 [DX3013]
uPD78F0533ADGK(A)@LQFP64 [DX3012]
uPD78F0533ADGK(A2)@LQFP64 [DX3012]
uPD78F0533ADGK@LQFP64 [DX3012]
uPD78F0533AGB(A)@LQFP64 [DX3011]
uPD78F0533AGB(A2)@LQFP64 [DX3011]
uPD78F0533AGB@LQFP64 [DX3011]
uPD78F0533AGC(A)@LQFP64 [DX3013]
uPD78F0533AGC(A2)@LQFP64 [DX3013]
uPD78F0533AGC@LQFP64 [DX3013]
uPD78F0533AGK(A)@LQFP64 [DX3012]
uPD78F0533AGK(A2)@LQFP64 [DX3012]
uPD78F0533AGK@LQFP64 [DX3012]
uPD78F0533DGA [DX3085]
uPD78F0533DGB(A)@LQFP64 [DX3011]
uPD78F0533DGB(A2)@LQFP64 [DX3011]
uPD78F0533DGB@LQFP64 [DX3011]
uPD78F0533DGC(A)@LQFP64 [DX3013]
uPD78F0533DGC(A2)@LQFP64 [DX3013]
uPD78F0533DGC@LQFP64 [DX3013]
uPD78F0533DGK(A)@LQFP64 [DX3012]
uPD78F0533DGK(A2)@LQFP64 [DX3012]
uPD78F0533DGK@LQFP64 [DX3012]
uPD78F0533GA [DX3085]
uPD78F0533GB(A)@LQFP64 [DX3011]
uPD78F0533GB(A2)@LQFP64 [DX3011]
uPD78F0533GB@LQFP64 [DX3011]
uPD78F0533GC(A)@LQFP64 [DX3013]
uPD78F0533GC(A2)@LQFP64 [DX3013]
uPD78F0533GC@LQFP64 [DX3013]

uPD78F0533GK(A)@LQFP64 [DX3012]
uPD78F0533GK(A2)@LQFP64 [DX3012]
uPD78F0533GK@LQFP64 [DX3012]
uPD78F0534AGB(A)@LQFP64 [DX3011]
uPD78F0534AGB(A2)@LQFP64 [DX3011]
uPD78F0534AGB@LQFP64 [DX3011]
uPD78F0534AGC(A)@LQFP64 [DX3013]
uPD78F0534AGC(A2)@LQFP64 [DX3013]
uPD78F0534AGC@LQFP64 [DX3013]
uPD78F0534AGK(A)@LQFP64 [DX3012]
uPD78F0534AGK(A2)@LQFP64 [DX3012]
uPD78F0534AGK@LQFP64 [DX3012]
uPD78F0534GA [DX3085]
uPD78F0534GB(A)@LQFP64 [DX3011]
uPD78F0534GB(A2)@LQFP64 [DX3011]
uPD78F0534GB@LQFP64 [DX3011]
uPD78F0534GC(A)@LQFP64 [DX3013]
uPD78F0534GC(A2)@LQFP64 [DX3013]
uPD78F0534GC@LQFP64 [DX3013]
uPD78F0534GK(A)@LQFP64 [DX3012]
uPD78F0534GK(A2)@LQFP64 [DX3012]
uPD78F0534GK@LQFP64 [DX3012]
uPD78F0535AGB(A)@LQFP64 [DX3011]
uPD78F0535AGB(A2)@LQFP64 [DX3011]
uPD78F0535AGB@LQFP64 [DX3011]
uPD78F0535AGC(A)@LQFP64 [DX3013]
uPD78F0535AGC(A2)@LQFP64 [DX3013]
uPD78F0535AGC@LQFP64 [DX3013]
uPD78F0535AGK(A)@LQFP64 [DX3012]
uPD78F0535AGK(A2)@LQFP64 [DX3012]
uPD78F0535AGK@LQFP64 [DX3012]
uPD78F0535GA [DX3085]
uPD78F0535GB(A)@LQFP64 [DX3011]
uPD78F0535GB(A2)@LQFP64 [DX3011]
uPD78F0535GB@LQFP64 [DX3011]
uPD78F0535GC(A)@LQFP64 [DX3013]
uPD78F0535GC(A2)@LQFP64 [DX3013]
uPD78F0535GC@LQFP64 [DX3013]
uPD78F0535GK(A)@LQFP64 [DX3012]
uPD78F0535GK(A2)@LQFP64 [DX3012]
uPD78F0535GK@LQFP64 [DX3012]
uPD78F0536AGB(A)@LQFP64 [DX3011]
uPD78F0536AGB(A2)@LQFP64 [DX3011]
uPD78F0536AGB@LQFP64 [DX3011]
uPD78F0536AGC(A)@LQFP64 [DX3013]
uPD78F0536AGC(A2)@LQFP64 [DX3013]
uPD78F0536AGC@LQFP64 [DX3013]
uPD78F0536AGK(A)@LQFP64 [DX3012]
uPD78F0536AGK(A2)@LQFP64 [DX3012]
uPD78F0536AGK@LQFP64 [DX3012]
uPD78F0536GA [DX3085]
uPD78F0536GB(A)@LQFP64 [DX3011]
uPD78F0536GB(A2)@LQFP64 [DX3011]
uPD78F0536GB@LQFP64 [DX3011]
uPD78F0536GC(A)@LQFP64 [DX3013]
uPD78F0536GC(A2)@LQFP64 [DX3013]
uPD78F0536GC@LQFP64 [DX3013]
uPD78F0536GK(A)@LQFP64 [DX3012]
uPD78F0536GK(A2)@LQFP64 [DX3012]
uPD78F0536GK@LQFP64 [DX3012]
uPD78F0537ADGB(A)@LQFP64 [DX3011]
uPD78F0537ADGB(A2)@LQFP64 [DX3011]
uPD78F0537ADGB@LQFP64 [DX3011]
uPD78F0537ADGC(A)@LQFP64 [DX3013]
uPD78F0537ADGC(A2)@LQFP64 [DX3013]
uPD78F0537ADGC@LQFP64 [DX3013]
uPD78F0537ADGK(A)@LQFP64 [DX3012]
uPD78F0537ADGK(A2)@LQFP64 [DX3012]
uPD78F0537ADGK@LQFP64 [DX3012]
uPD78F0537AGB(A)@LQFP64 [DX3011]
uPD78F0537AGB(A2)@LQFP64 [DX3011]
uPD78F0537AGB@LQFP64 [DX3011]
uPD78F0537AGC(A)@LQFP64 [DX3013]
uPD78F0537AGC(A2)@LQFP64 [DX3013]
uPD78F0537AGC@LQFP64 [DX3013]
uPD78F0537AGK(A)@LQFP64 [DX3012]

uPD78F0537AGK(A2)@LQFP64 [DX3012]
uPD78F0537AGK@LQFP64 [DX3012]
uPD78F0537DGA [DX3085]
uPD78F0537DGB(A)@LQFP64 [DX3011]
uPD78F0537DGB(A2)@LQFP64 [DX3011]
uPD78F0537DGB@LQFP64 [DX3011]
uPD78F0537DGC(A)@LQFP64 [DX3013]
uPD78F0537DGC(A2)@LQFP64 [DX3013]
uPD78F0537DGC@LQFP64 [DX3013]
uPD78F0537DGK(A)@LQFP64 [DX3012]
uPD78F0537DGK(A2)@LQFP64 [DX3012]
uPD78F0537DGK@LQFP64 [DX3012]
uPD78F0537GA [DX3085]
uPD78F0537GB(A)@LQFP64 [DX3011]
uPD78F0537GB(A2)@LQFP64 [DX3011]
uPD78F0537GB@LQFP64 [DX3011]
uPD78F0537GC(A)@LQFP64 [DX3013]
uPD78F0537GC(A2)@LQFP64 [DX3013]
uPD78F0537GC@LQFP64 [DX3013]
uPD78F0537GK(A)@LQFP64 [DX3012]
uPD78F0537GK(A2)@LQFP64 [DX3012]
uPD78F0537GK@LQFP64 [DX3012]
uPD78F0544AGC(A)@LQFP80 [DX3017]
uPD78F0544AGC(A2)@LQFP80 [DX3017]
uPD78F0544AGC@LQFP80 [DX3017]
uPD78F0544AGK(A)@LQFP80 [DX3016]
uPD78F0544AGK(A2)@LQFP80 [DX3016]
uPD78F0544AGK@LQFP80 [DX3016]
uPD78F0544GC(A)@LQFP80 [DX3017]
uPD78F0544GC(A2)@LQFP80 [DX3017]
uPD78F0544GC@LQFP80 [DX3017]
uPD78F0544GK(A)@LQFP80 [DX3016]
uPD78F0544GK(A2)@LQFP80 [DX3016]
uPD78F0544GK@LQFP80 [DX3016]
uPD78F0545AGC(A)@LQFP80 [DX3017]
uPD78F0545AGC(A2)@LQFP80 [DX3017]
uPD78F0545AGC@LQFP80 [DX3017]
uPD78F0545AGK(A)@LQFP80 [DX3016]
uPD78F0545AGK(A2)@LQFP80 [DX3016]
uPD78F0545AGK@LQFP80 [DX3016]
uPD78F0545GC(A)@LQFP80 [DX3017]
uPD78F0545GC(A2)@LQFP80 [DX3017]
uPD78F0545GC@LQFP80 [DX3017]
uPD78F0545GK(A)@LQFP80 [DX3016]
uPD78F0545GK(A2)@LQFP80 [DX3016]
uPD78F0545GK@LQFP80 [DX3016]
uPD78F0546AGK(A)@LQFP80 [DX3016]
uPD78F0546AGK(A2)@LQFP80 [DX3016]
uPD78F0546AGK@LQFP80 [DX3016]
uPD78F0546GK(A)@LQFP80 [DX3016]
uPD78F0546GK(A2)@LQFP80 [DX3016]
uPD78F0546GK@LQFP80 [DX3016]
uPD78F0547ADGC(A)@LQFP80 [DX3017]
uPD78F0547ADGC(A2)@LQFP80 [DX3017]
uPD78F0547ADGC@LQFP80 [DX3017]
uPD78F0547ADGK(A)@LQFP80 [DX3016]
uPD78F0547ADGK(A2)@LQFP80 [DX3016]
uPD78F0547ADGK@LQFP80 [DX3016]
uPD78F0547AGC(A)@LQFP80 [DX3017]
uPD78F0547AGC(A2)@LQFP80 [DX3017]
uPD78F0547AGC@LQFP80 [DX3017]
uPD78F0547AGK(A)@LQFP80 [DX3016]
uPD78F0547AGK(A2)@LQFP80 [DX3016]
uPD78F0547AGK@LQFP80 [DX3016]
uPD78F0547DGC(A)@LQFP80 [DX3017]
uPD78F0547DGC(A2)@LQFP80 [DX3017]
uPD78F0547DGC@LQFP80 [DX3017]
uPD78F0547DGK(A)@LQFP80 [DX3016]
uPD78F0547DGK(A2)@LQFP80 [DX3016]
uPD78F0547DGK@LQFP80 [DX3016]
uPD78F0547GC(A)@LQFP80 [DX3017]
uPD78F0547GC(A2)@LQFP80 [DX3017]
uPD78F0547GC@LQFP80 [DX3017]
uPD78F0547GK(A)@LQFP80 [DX3016]
uPD78F0547GK(A2)@LQFP80 [DX3016]
uPD78F0547GK@LQFP80 [DX3016]
uPD78F0550MA@SSOP16 [DX1016]

uPD78F0550MC@SSOP16 [DX1016]
uPD78F0551MC@SSOP16 [DX1016]
uPD78F0552MC@SSOP16 [DX1016]
uPD78F0553MC@SSOP16 [DX1016]
uPD78F0555MC@SSOP16 [DX1016]
uPD78F0556MC@SSOP16 [DX1016]
uPD78F0557MC@SSOP16 [DX1016]
uPD78F0558MC@SSOP16 [DX1016]
uPD78F0560K@WQFN32 [DX4015]
uPD78F0561FC@FLGA25 [DX0001]
uPD78F0561MC@SSOP20 [DX1027]
uPD78F0562K@WQFN32 [DX4015]
uPD78F0563FC@FLGA25 [DX0001]
uPD78F0563MC@SSOP20 [DX1027]
uPD78F0565K@WQFN32 [DX4015]
uPD78F0566FC@FLGA25 [DX0001]
uPD78F0566MC@SSOP20 [DX1027]
uPD78F0567K@WQFN32 [DX4015]
uPD78F0568FC@FLGA25 [DX0001]
uPD78F0568MC@SSOP20 [DX1027]
uPD78F0571MC@SSOP30 [DX1027]
uPD78F0573MC@SSOP30 [DX1027]
uPD78F0576MC@SSOP30 [DX1027]
uPD78F0578MC@SSOP30 [DX1027]
uPD78F0580GB@LQFP44 [DX3005]
uPD78F0581GA@LQFP48 [DX3047]
uPD78F0581K@WQFN40 [DX4017]
uPD78F0582GB@LQFP44 [DX3005]
uPD78F0583GA@LQFP48 [DX3047]
uPD78F0583K@WQFN40 [DX4017]
uPD78F0585GB@LQFP44 [DX3005]
uPD78F0586GA@LQFP48 [DX3047]
uPD78F0586K@WQFN40 [DX4017]
uPD78F0587GB@LQFP44 [DX3005]
uPD78F0588GA@LQFP48 [DX3047]
uPD78F0588K@WQFN40 [DX4017]
uPD78F0591 [DX1027]
uPD78F0593 [DX3047]
uPD78F0740MA [DX1016]
uPD78F0742MA [DX1016]
uPD78F0744MC [DX1027]
uPD78F0746MC [DX1027]
uPD78F0751MA [DX1016]
uPD78F0753MC [DX1027]
uPD78F0755MC [DX1027]
uPD78F0760 [DX3047]
uPD78F0762 [DX3047]
uPD78F0764 [DX3011]
uPD78F0551MA@SSOP16 [DX1016]
uPD78F0552MA@SSOP16 [DX1016]
uPD78F0553MA@SSOP16 [DX1016]
uPD78F0555MA@SSOP16 [DX1016]
uPD78F0556MA@SSOP16 [DX1016]
uPD78F0557MA@SSOP16 [DX1016]
uPD78F0558MA@SSOP16 [DX1016]
uPD78F0560FC@FLGA25 [DX0001]
uPD78F0560MC@SSOP20 [DX1027]
uPD78F0561K@WQFN32 [DX4015]
uPD78F0562FC@FLGA25 [DX0001]
uPD78F0562MC@SSOP20 [DX1027]
uPD78F0563K@WQFN32 [DX4015]
uPD78F0565FC@FLGA25 [DX0001]
uPD78F0565MC@SSOP20 [DX1027]
uPD78F0566K@WQFN32 [DX4015]
uPD78F0567FC@FLGA25 [DX0001]
uPD78F0567MC@SSOP20 [DX1027]
uPD78F0568K@WQFN32 [DX4015]
uPD78F0570MC@SSOP30 [DX1027]
uPD78F0572MC@SSOP30 [DX1027]
uPD78F0575MC@SSOP30 [DX1027]
uPD78F0577MC@SSOP30 [DX1027]
uPD78F0580GA@LQFP48 [DX3047]
uPD78F0580K@WQFN40 [DX4017]
uPD78F0581GB@LQFP44 [DX3005]
uPD78F0582GA@LQFP48 [DX3047]
uPD78F0582K@WQFN40 [DX4017]
uPD78F0583GB@LQFP44 [DX3005]
uPD78F0585GA@LQFP48 [DX3047]
uPD78F0585K@WQFN40 [DX4017]
uPD78F0586GB@LQFP44 [DX3005]
uPD78F0587GA@LQFP48 [DX3047]
uPD78F0587K@WQFN40 [DX4017]
uPD78F0588GB@LQFP44 [DX3005]
uPD78F0590 [DX1027]
uPD78F0592 [DX3047]
uPD78F0730 [DX1027]
uPD78F0741MA [DX1016]
uPD78F0743MC [DX1027]
uPD78F0745MC [DX1027]
uPD78F0750MA [DX1016]
uPD78F0752MA [DX1016]
uPD78F0754MC [DX1027]
uPD78F0756MC [DX1027]
uPD78F0761 [DX3047]
uPD78F0763 [DX3011]
uPD78F0765 [DX3011]

uPD78F0820B(A)@LQFP100 [DX3043]
uPD78F0820B(A1)@LQFP100 [DX3043]
uPD78F0820B(A2)@LQFP100 [DX3043]
uPD78F0820B@LQFP100 [DX3043]
uPD78F0822B(A)@LQFP100 [DX3043]
uPD78F0822B(A1)@LQFP100 [DX3043]
uPD78F0822B(A2)@LQFP100 [DX3043]
uPD78F0822B@LQFP100 [DX3043]
uPD78F0824AGC(A)@QFP80 [DX3018]
uPD78F0824AGC(A1)@QFP80 [DX3018]
uPD78F0824AGC(A2)@QFP80 [DX3018]
uPD78F0824AGC@QFP80 [DX3018]
uPD78F0824BGC(A)@QFP80 [DX3018]
uPD78F0824BGC(A1)@QFP80 [DX3018]
uPD78F0824BGC(A2)@QFP80 [DX3018]
uPD78F0824BGC@QFP80 [DX3018]
uPD78F0826AGC(A)@QFP80 [DX3018]
uPD78F0826AGC(A1)@QFP80 [DX3018]
uPD78F0826AGC(A2)@QFP80 [DX3018]
uPD78F0826AGC@QFP80 [DX3018]
uPD78F0826BGC(A)@QFP80 [DX3018]
uPD78F0826BGC(A1)@QFP80 [DX3018]
uPD78F0826BGC(A2)@QFP80 [DX3018]
uPD78F0826BGC@QFP80 [DX3018]
uPD78F0828AGC(A)@QFP80 [DX3018]
uPD78F0828AGC(A1)@QFP80 [DX3018]
uPD78F0828AGC(A2)@QFP80 [DX3018]
uPD78F0828AGC@QFP80 [DX3018]
uPD78F0828BGC(A)@QFP80 [DX3018]
uPD78F0828BGC(A1)@QFP80 [DX3018]
uPD78F0828BGC(A2)@QFP80 [DX3018]
uPD78F0828BGC@QFP80 [DX3018]
uPD78F0836GB(A)@LQFP64 [DX3011]
uPD78F0836GB(A2)@LQFP64 [DX3011]
uPD78F0836GB@LQFP64 [DX3011]
uPD78F0837GB(A)@LQFP64 [DX3011]
uPD78F0837GB(A2)@LQFP64 [DX3011]
uPD78F0837GB@LQFP64 [DX3011]
uPD78F0838GK(A)@LQFP80 [DX3016]
uPD78F0838GK(A2)@LQFP80 [DX3016]
uPD78F0838GK@LQFP80 [DX3016]
uPD78F0839GK(A)@LQFP80 [DX3016]
uPD78F0839GK(A2)@LQFP80 [DX3016]
uPD78F0839GK@LQFP80 [DX3016]
uPD78F0840GK(A)@LQFP80 [DX3016]
uPD78F0840GK(A2)@LQFP80 [DX3016]
uPD78F0840GK@LQFP80 [DX3016]
uPD78F0841GK(A)@LQFP80 [DX3016]
uPD78F0841GK(A2)@LQFP80 [DX3016]
uPD78F0841GK@LQFP80 [DX3016]
uPD78F0842GK(A)@LQFP80 [DX3016]
uPD78F0842GK(A2)@LQFP80 [DX3016]
uPD78F0842GK@LQFP80 [DX3016]
uPD78F0843GK(A)@LQFP80 [DX3016]
uPD78F0843GK(A2)@LQFP80 [DX3016]
uPD78F0843GK@LQFP80 [DX3016]
uPD78F0844GB(A)@LQFP64 [DX3011]
uPD78F0844GB(A2)@LQFP64 [DX3011]
uPD78F0844GB@LQFP64 [DX3011]
uPD78F0845GB(A)@LQFP64 [DX3011]
uPD78F0845GB(A2)@LQFP64 [DX3011]
uPD78F0845GB@LQFP64 [DX3011]
uPD78F0846GK(A)@LQFP80 [DX3016]
uPD78F0846GK(A2)@LQFP80 [DX3016]
uPD78F0846GK@LQFP80 [DX3016]
uPD78F0847GK(A)@LQFP80 [DX3016]
uPD78F0847GK(A2)@LQFP80 [DX3016]
uPD78F0847GK@LQFP80 [DX3016]
uPD78F0848GK(A)@LQFP80 [DX3016]
uPD78F0848GK(A2)@LQFP80 [DX3016]
uPD78F0848GK@LQFP80 [DX3016]
uPD78F0849GK(A)@LQFP80 [DX3016]
uPD78F0849GK(A2)@LQFP80 [DX3016]
uPD78F0849GK@LQFP80 [DX3016]
uPD78F0854MA [DX1001]
uPD78F0855MA [DX1001]
uPD78F0856MA [DX1001]
uPD78F0857MC [DX1027]
uPD78F0858MC [DX1027]
uPD78F0859MC [DX1027]
uPD78F0864MC [DX1027]
uPD78F0865MC [DX1027]
uPD78F0881AGBA [DX3002]
uPD78F0881AGBA2 [DX3002]
uPD78F0882AGBA [DX3002]
uPD78F0882AGBA2 [DX3002]
uPD78F0883AGBA [DX3002]
uPD78F0883AGBA2 [DX3002]
uPD78F0884AGAA [DX3007]
uPD78F0884AGAA2 [DX3007]
uPD78F0885AGAA [DX3007]
uPD78F0885AGAA2 [DX3007]
uPD78F0886AGAA [DX3007]
uPD78F0886AGAA2 [DX3007]
uPD78F0887AGBA [DX3011]
uPD78F0887AGBA2 [DX3011]

uPD78F0887AGKA [DX3012]
uPD78F0888AGBA [DX3011]
uPD78F0888AGKA [DX3012]
uPD78F0889AGBA [DX3011]
uPD78F0889AGKA [DX3012]
uPD78F0890AGBA [DX3011]
uPD78F0890AGKA [DX3012]
uPD78F0891AGCA [DX3016]
uPD78F0891AGKA [DX3018]
uPD78F0892AGCA [DX3016]
uPD78F0892AGKA [DX3018]
uPD78F0893AGCA [DX3016]
uPD78F0893AGKA [DX3018]
uPD78F0894AGAA [DX3007]
uPD78F0895AGAA [DX3007]
uPD78F1142AGA@TQFP64 [DX3064]
uPD78F1142AGK@LQFP64 [DX3012]
uPD78F1142GB@LQFP64 [DX3011]
uPD78F1143AGA@TQFP64 [DX3064]
uPD78F1143AGK [DX3012]
uPD78F1143GB@LQFP64 [DX3011]
uPD78F1144AGA [DX3064]
uPD78F1144AGK [DX3012]
uPD78F1144GB@LQFP64 [DX3011]
uPD78F1145AGA [DX3064]
uPD78F1145AGK [DX3012]
uPD78F1145GB@LQFP64 [DX3011]
uPD78F1146AGA [DX3064]
uPD78F1146AGK [DX3012]
uPD78F1146GB@LQFP64 [DX3011]
uPD78F1152AGC [DX3018]
uPD78F1152GC@LQFP80 [DX3018]
uPD78F1153AGC [DX3018]
uPD78F1153GC@LQFP80 [DX3018]
uPD78F1154AGC [DX3018]
uPD78F1154GC@LQFP80 [DX3018]
uPD78F1155AGC [DX3018]
uPD78F1155GC@LQFP80 [DX3018]
uPD78F1156AGC [DX3018]
uPD78F1156GC@LQFP80 [DX3018]
uPD78F1162@LQFP100 [DX3062]
uPD78F1162AGC [DX3043]
uPD78F1162GC@LQFP100 [DX3043]
uPD78F1163@LQFP100 [DX3062]
uPD78F1163AGC [DX3043]
uPD78F1163GC@LQFP100 [DX3043]
uPD78F1164@LQFP100 [DX3062]
uPD78F1164AGC [DX3023]
uPD78F0887AGKA2 [DX3012]
uPD78F0888AGBA2 [DX3011]
uPD78F0888AGKA2 [DX3012]
uPD78F0889AGBA2 [DX3011]
uPD78F0889AGKA2 [DX3012]
uPD78F0890AGBA2 [DX3011]
uPD78F0890AGKA2 [DX3012]
uPD78F0891AGCA2 [DX3016]
uPD78F0891AGKA2 [DX3018]
uPD78F0892AGCA2 [DX3016]
uPD78F0892AGKA2 [DX3018]
uPD78F0893AGCA2 [DX3016]
uPD78F0893AGKA2 [DX3018]
uPD78F0894AGAA2 [DX3007]
uPD78F0895AGAA2 [DX3007]
uPD78F1142AGB@LQFP64 [DX3011]
uPD78F1142GA@TQFP64 [DX3064]
uPD78F1142GK@LQFP64 [DX3012]
uPD78F1143AGB [DX3011]
uPD78F1143GA@TQFP64 [DX3064]
uPD78F1143GK@LQFP64 [DX3012]
uPD78F1144AGB [DX3011]
uPD78F1144GA@TQFP64 [DX3064]
uPD78F1144GK@LQFP64 [DX3012]
uPD78F1145AGB [DX3011]
uPD78F1145GA@TQFP64 [DX3064]
uPD78F1145GK@LQFP64 [DX3012]
uPD78F1146AGB [DX3011]
uPD78F1146GA@TQFP64 [DX3064]
uPD78F1146GK@LQFP64 [DX3012]
uPD78F1152AGK [DX3016]
uPD78F1152GK@LQFP80 [DX3016]
uPD78F1153AGK [DX3016]
uPD78F1153GK@LQFP80 [DX3016]
uPD78F1154AGK [DX3016]
uPD78F1154GK@LQFP80 [DX3016]
uPD78F1155AGK [DX3016]
uPD78F1155GK@LQFP80 [DX3016]
uPD78F1156AGK [DX3016]
uPD78F1156GK@LQFP80 [DX3016]
uPD78F1162A [DX3062]
uPD78F1162AGF [DX3062]
uPD78F1162GF@LQFP100 [DX3062]
uPD78F1163A [DX3062]
uPD78F1163AGF [DX3062]
uPD78F1163GF@LQFP100 [DX3062]
uPD78F1164A [DX3062]
uPD78F1164AGF [DX3062]

uPD78F1164GC@LQFP100 [DX3023]
uPD78F1164GF@LQFP100 [DX3062]
uPD78F1165@LQFP100 [DX3062]
uPD78F1165A [DX3062]
uPD78F1165AGC [DX3043]
uPD78F1165AGF [DX3062]
uPD78F1165GC@LQFP100 [DX3043]
uPD78F1165GF@LQFP100 [DX3062]
uPD78F1166@LQFP100 [DX3062]
uPD78F1166A [DX3062]
uPD78F1166AGC [DX3043]
uPD78F1166AGF [DX3062]
uPD78F1166GC@LQFP100 [DX3043]
uPD78F1166GF@LQFP100 [DX3062]
uPD78F1167@LQFP100 [DX3062]
uPD78F1167A [DX3062]
uPD78F1167AGC [DX3043]
uPD78F1167AGF [DX3062]
uPD78F1167GC@LQFP100 [DX3043]
uPD78F1167GF@LQFP100 [DX3062]
uPD78F1168@LQFP100 [DX3062]
uPD78F1168A [DX3062]
uPD78F1168AGC [DX3043]
uPD78F1168AGF [DX3062]
uPD78F1168GC@LQFP100 [DX3043]
uPD78F1168GF@LQFP100 [DX3062]
uPD78F1174AGF(A)@LQFP128 [DX3031]
uPD78F1174AGF@LQFP128 [DX3031]
uPD78F1174GF@LQFP128 [DX3031]
uPD78F1175AGF(A)@LQFP128 [DX3031]
uPD78F1175AGF@LQFP128 [DX3031]
uPD78F1175GF@LQFP128 [DX3031]
uPD78F1176AGF(A)@LQFP128 [DX3031]
uPD78F1176AGF@LQFP128 [DX3031]
uPD78F1176GF@LQFP128 [DX3031]
uPD78F1177AGF(A)@LQFP128 [DX3031]
uPD78F1177AGF@LQFP128 [DX3031]
uPD78F1177GF@LQFP128 [DX3031]
uPD78F1178AGF(A)@LQFP128 [DX3031]
uPD78F1178AGF@LQFP128 [DX3031]
uPD78F1178GF@LQFP128 [DX3031]
uPD78F1184AGF(A)@LQFP144 [DX3051]
uPD78F1184AGF@LQFP144 [DX3051]
uPD78F1184GF@LQFP144 [DX3051]
uPD78F1185AGF(A)@LQFP144 [DX3051]
uPD78F1185AGF@LQFP144 [DX3051]
uPD78F1185GF@LQFP144 [DX3051]
uPD78F1186AGF(A)@LQFP144 [DX3051]
uPD78F1186AGF@LQFP144 [DX3051]
uPD78F1186GF@LQFP144 [DX3051]
uPD78F1187AGF(A)@LQFP144 [DX3051]
uPD78F1187AGF@LQFP144 [DX3051]
uPD78F1187GF@LQFP144 [DX3051]
uPD78F1188AGF(A)@LQFP144 [DX3051]
uPD78F1188AGF@LQFP144 [DX3051]
uPD78F1188GF@LQFP144 [DX3051]
uPD78F1201MC@SSOP30 [DX1027]
uPD78F1203MC@SSOP30 [DX1027]
uPD78F1204MC@SSOP30 [DX1027]
uPD78F1205MC@SSOP30 [DX1027]
uPD78F1211GA@QFP48 [DX3007]
uPD78F1211GB@QFP44 [DX3002]
uPD78F1211MC@SSOP38 [DX1027]
uPD78F1213GA@QFP48 [DX3007]
uPD78F1213GB@QFP44 [DX3002]
uPD78F1213MC@SSOP38 [DX1027]
uPD78F1214GA@QFP48 [DX3007]
uPD78F1214GB@QFP44 [DX3002]
uPD78F1214MC@SSOP38 [DX1027]
uPD78F1215GA@QFP48 [DX3007]
uPD78F1215GB@QFP44 [DX3002]
uPD78F1215MC@SSOP38 [DX1027]
uPD78F1221GB@QFP52 [DX3009]
uPD78F1223GB@QFP52 [DX3009]
uPD78F1224GB@QFP52 [DX3009]
uPD78F1225GB@QFP52 [DX3009]
uPD78F1231GB@QFP64 [DX3011]
uPD78F1231GK@QFP64 [DX3064]
uPD78F1233GB@QFP64 [DX3011]
uPD78F1233GK@QFP64 [DX3064]
uPD78F1234GB@QFP64 [DX3011]
uPD78F1234GK@QFP64 [DX3064]
uPD78F1235GB@QFP64 [DX3011]
uPD78F1235GK@QFP64 [DX3064]
uPD78F1804AK8 [DX4015]
uPD78F1804AK8A [DX4015]

uPD78F1804AK8A2 [DX4015]
uPD78F1804AMC [DX1027]
uPD78F1804AMCA [DX1027]
uPD78F1804AMCA2 [DX1027]
uPD78F1804K8 [DX4015]
uPD78F1804K8A [DX4015]
uPD78F1804K8A2 [DX4015]
uPD78F1804MC [DX1027]
uPD78F1804MCA [DX1027]
uPD78F1804MCA2 [DX1027]
uPD78F1805AK8 [DX4015]
uPD78F1805AK8A [DX4015]
uPD78F1805AK8A2 [DX4015]
uPD78F1805AMC [DX1027]
uPD78F1805AMCA [DX1027]
uPD78F1805AMCA2 [DX1027]
uPD78F1805K8 [DX4015]
uPD78F1805K8A [DX4015]
uPD78F1805K8A2 [DX4015]
uPD78F1805MC [DX1027]
uPD78F1805MCA [DX1027]
uPD78F1805MCA2 [DX1027]
uPD78F1806AK8 [DX4015]
uPD78F1806AK8A [DX4015]
uPD78F1806AK8A2 [DX4015]
uPD78F1806AMC [DX1027]
uPD78F1806AMCA [DX1027]
uPD78F1806AMCA2 [DX1027]
uPD78F1806K8 [DX4015]
uPD78F1806K8A [DX4015]
uPD78F1806K8A2 [DX4015]
uPD78F1806MC [DX1027]
uPD78F1806MCA [DX1027]
uPD78F1806MCA2 [DX1027]
uPD78F1807AK8 [DX4015]
uPD78F1807AK8A [DX4015]
uPD78F1807AK8A2 [DX4015]
uPD78F1807AMC [DX1027]
uPD78F1807AMCA [DX1027]
uPD78F1807AMCA2 [DX1027]
uPD78F1807K8 [DX4015]
uPD78F1807K8A [DX4015]
uPD78F1807K8A2 [DX4015]
uPD78F1807MC [DX1027]
uPD78F1807MCA [DX1027]
uPD78F1807MCA2 [DX1027]
uPD78F1808AK8 [DX4017]
uPD78F1808AK8A [DX4017]
uPD78F1808AK8A2 [DX4017]
uPD78F1808K8 [DX4017]
uPD78F1808K8A [DX4017]
uPD78F1808K8A2 [DX4017]
uPD78F1809AK8 [DX4017]
uPD78F1809AK8A [DX4017]
uPD78F1809AK8A2 [DX4017]
uPD78F1809K8 [DX4017]
uPD78F1809K8A [DX4017]
uPD78F1809K8A2 [DX4017]
uPD78F1810AK8 [DX4017]
uPD78F1810AK8A [DX4017]
uPD78F1810AK8A2 [DX4017]
uPD78F1810K8 [DX4017]
uPD78F1810K8A [DX4017]
uPD78F1810K8A2 [DX4017]
uPD78F1811AK8 [DX4017]
uPD78F1811AK8A [DX4017]
uPD78F1811AK8A2 [DX4017]
uPD78F1811K8 [DX4017]
uPD78F1811K8A [DX4017]
uPD78F1811K8A2 [DX4017]
uPD78F1812AGA [DX3007]
uPD78F1812AGAA [DX3007]
uPD78F1812AGAA2 [DX3007]
uPD78F1812AK8 [DX3007]
uPD78F1812AK8A [DX3007]
uPD78F1812AK8A2 [DX3007]
uPD78F1812GA [DX3007]
uPD78F1812GAA [DX3007]
uPD78F1812GAA2 [DX3007]
uPD78F1812K8 [DX3007]
uPD78F1812K8A [DX3007]
uPD78F1812K8A2 [DX3007]
uPD78F1813AGA [DX3007]
uPD78F1813AGAA [DX3007]
uPD78F1813AGAA2 [DX3007]
uPD78F1813AK8 [DX3007]
uPD78F1813AK8A [DX3007]
uPD78F1813AK8A2 [DX3007]
uPD78F1813GA [DX3007]
uPD78F1813GAA [DX3007]
uPD78F1813GAA2 [DX3007]
uPD78F1813K8 [DX3007]
uPD78F1813K8A [DX3007]
uPD78F1813K8A2 [DX3007]
uPD78F1814AGA [DX3007]
uPD78F1814AGAA [DX3007]

uPD78F1814AGAA2 [DX3007]
uPD78F1814AK8 [DX3007]
uPD78F1814AK8A [DX3007]
uPD78F1814AK8A2 [DX3007]
uPD78F1814GA [DX3007]
uPD78F1814GAA [DX3007]
uPD78F1814GAA2 [DX3007]
uPD78F1814K8 [DX3007]
uPD78F1814K8A [DX3007]
uPD78F1814K8A2 [DX3007]
uPD78F1815AGA [DX3007]
uPD78F1815AGAA [DX3007]
uPD78F1815AGAA2 [DX3007]
uPD78F1815AK8 [DX3007]
uPD78F1815AK8A [DX3007]
uPD78F1815AK8A2 [DX3007]
uPD78F1815GA [DX3007]
uPD78F1815GAA [DX3007]
uPD78F1815GAA2 [DX3007]
uPD78F1815K8 [DX3007]
uPD78F1815K8A [DX3007]
uPD78F1815K8A2 [DX3007]
uPD78F1816AGA [DX3007]
uPD78F1816AGAA [DX3007]
uPD78F1816AGAA2 [DX3007]
uPD78F1816AK8 [DX3007]
uPD78F1816AK8A [DX3007]
uPD78F1816AK8A2 [DX3007]
uPD78F1816GA [DX3007]
uPD78F1816GAA [DX3007]
uPD78F1816GAA2 [DX3007]
uPD78F1816K8 [DX3007]
uPD78F1816K8A [DX3007]
uPD78F1816K8A2 [DX3007]
uPD78F1817AGA [DX3007]
uPD78F1817AGAA [DX3007]
uPD78F1817AGAA2 [DX3007]
uPD78F1817AK8 [DX3007]
uPD78F1817AK8A [DX3007]
uPD78F1817AK8A2 [DX3007]
uPD78F1817GA [DX3007]
uPD78F1817GAA [DX3007]
uPD78F1817GAA2 [DX3007]
uPD78F1817K8 [DX3007]
uPD78F1817K8A [DX3007]
uPD78F1817K8A2 [DX3007]
uPD78F1818AGB [DX3011]
uPD78F1818AGBA [DX3011]
uPD78F1818AGBA2 [DX3011]
uPD78F1818GB [DX3011]
uPD78F1818GBA [DX3011]
uPD78F1818GBA2 [DX3011]
uPD78F1819AGB [DX3011]
uPD78F1819AGBA [DX3011]
uPD78F1819AGBA2 [DX3011]
uPD78F1819GB [DX3011]
uPD78F1819GBA [DX3011]
uPD78F1819GBA2 [DX3011]
uPD78F1820AGB [DX3011]
uPD78F1820AGBA [DX3011]
uPD78F1820AGBA2 [DX3011]
uPD78F1820GB [DX3011]
uPD78F1820GBA [DX3011]
uPD78F1820GBA2 [DX3011]
uPD78F1821AGB [DX3011]
uPD78F1821AGBA [DX3011]
uPD78F1821AGBA2 [DX3011]
uPD78F1821GB [DX3011]
uPD78F1821GBA [DX3011]
uPD78F1821GBA2 [DX3011]
uPD78F1822AGB [DX3011]
uPD78F1822AGBA [DX3011]
uPD78F1822AGBA2 [DX3011]
uPD78F1822GB [DX3011]
uPD78F1822GBA [DX3011]
uPD78F1822GBA2 [DX3011]
uPD78F1823AGK [DX3016]
uPD78F1823AGKA [DX3016]
uPD78F1823AGKA2 [DX3016]
uPD78F1823GK [DX3016]
uPD78F1823GKA [DX3016]
uPD78F1823GKA2 [DX3016]
uPD78F1824AGK [DX3016]
uPD78F1824AGKA [DX3016]
uPD78F1824AGKA2 [DX3016]
uPD78F1824GK [DX3016]
uPD78F1824GKA [DX3016]
uPD78F1824GKA2 [DX3016]
uPD78F1825AGK [DX3016]
uPD78F1825AGKA [DX3016]
uPD78F1825AGKA2 [DX3016]
uPD78F1825GK [DX3016]
uPD78F1825GKA [DX3016]
uPD78F1825GKA2 [DX3016]
uPD78F1826AGA [DX3007]
uPD78F1826AGAA [DX3007]

uPD78F1826AGAA2 [DX3007]
uPD78F1826AK8 [DX3007]
uPD78F1826AK8A [DX3007]
uPD78F1826AK8A2 [DX3007]
uPD78F1826GA [DX3007]
uPD78F1826GAA [DX3007]
uPD78F1826GAA2 [DX3007]
uPD78F1826K8 [DX3007]
uPD78F1826K8A [DX3007]
uPD78F1826K8A2 [DX3007]
uPD78F1827AGA [DX3007]
uPD78F1827AGAA [DX3007]
uPD78F1827AGAA2 [DX3007]
uPD78F1827AK8 [DX3007]
uPD78F1827AK8A [DX3007]
uPD78F1827AK8A2 [DX3007]
uPD78F1827GA [DX3007]
uPD78F1827GAA [DX3007]
uPD78F1827GAA2 [DX3007]
uPD78F1827K8 [DX3007]
uPD78F1827K8A [DX3007]
uPD78F1827K8A2 [DX3007]
uPD78F1828AGA [DX3007]
uPD78F1828AGAA [DX3007]
uPD78F1828AGAA2 [DX3007]
uPD78F1828AK8 [DX3007]
uPD78F1828AK8A [DX3007]
uPD78F1828AK8A2 [DX3007]
uPD78F1828GA [DX3007]
uPD78F1828GAA [DX3007]
uPD78F1828GAA2 [DX3007]
uPD78F1828K8 [DX3007]
uPD78F1828K8A [DX3007]
uPD78F1828K8A2 [DX3007]
uPD78F1829AGA [DX3007]
uPD78F1829AGAA [DX3007]
uPD78F1829AGAA2 [DX3007]
uPD78F1829AK8 [DX3007]
uPD78F1829AK8A [DX3007]
uPD78F1829AK8A2 [DX3007]
uPD78F1829GA [DX3007]
uPD78F1829GAA [DX3007]
uPD78F1829GAA2 [DX3007]
uPD78F1829K8 [DX3007]
uPD78F1829K8A [DX3007]
uPD78F1829K8A2 [DX3007]
uPD78F1830AGA [DX3007]
uPD78F1830AGAA [DX3007]
uPD78F1830AGAA2 [DX3007]
uPD78F1830AK8 [DX3007]
uPD78F1830AK8A [DX3007]
uPD78F1830AK8A2 [DX3007]
uPD78F1830GA [DX3007]
uPD78F1830GAA [DX3007]
uPD78F1830GAA2 [DX3007]
uPD78F1830K8 [DX3007]
uPD78F1830K8A [DX3007]
uPD78F1830K8A2 [DX3007]
uPD78F1831AGB [DX3011]
uPD78F1831AGBA [DX3011]
uPD78F1831AGBA2 [DX3011]
uPD78F1831GB [DX3011]
uPD78F1831GBA [DX3011]
uPD78F1831GBA2 [DX3011]
uPD78F1832AGB [DX3011]
uPD78F1832AGBA [DX3011]
uPD78F1832AGBA2 [DX3011]
uPD78F1832GB [DX3011]
uPD78F1832GBA [DX3011]
uPD78F1832GBA2 [DX3011]
uPD78F1833AGB [DX3011]
uPD78F1833AGBA [DX3011]
uPD78F1833AGBA2 [DX3011]
uPD78F1833GB [DX3011]
uPD78F1833GBA [DX3011]
uPD78F1833GBA2 [DX3011]
uPD78F1834AGB [DX3011]
uPD78F1834AGBA [DX3011]
uPD78F1834AGBA2 [DX3011]
uPD78F1834GB [DX3011]
uPD78F1834GBA [DX3011]
uPD78F1834GBA2 [DX3011]
uPD78F1835AGB [DX3011]
uPD78F1835AGBA [DX3011]
uPD78F1835AGBA2 [DX3011]
uPD78F1835GB [DX3011]
uPD78F1835GBA [DX3011]
uPD78F1835GBA2 [DX3011]
uPD78F1836AGK [DX3016]
uPD78F1836AGKA [DX3016]
uPD78F1836AGKA2 [DX3016]
uPD78F1836GK [DX3016]
uPD78F1836GKA [DX3016]
uPD78F1836GKA2 [DX3016]
uPD78F1837AGK [DX3016]
uPD78F1837AGKA [DX3016]

uPD78F1837AGKA2 [DX3016]
uPD78F1837GK [DX3016]
uPD78F1837GKA [DX3016]
uPD78F1837GKA2 [DX3016]
uPD78F1838AGK [DX3016]
uPD78F1838AGKA [DX3016]
uPD78F1838AGKA2 [DX3016]
uPD78F1838GK [DX3016]
uPD78F1838GKA [DX3016]
uPD78F1838GKA2 [DX3016]
uPD78F1839AGK [DX3016]
uPD78F1839AGKA [DX3016]
uPD78F1839AGKA2 [DX3016]
uPD78F1839GK [DX3016]
uPD78F1839GKA [DX3016]
uPD78F1839GKA2 [DX3016]
uPD78F1840AGK [DX3021]
uPD78F1840AGKA [DX3021]
uPD78F1840AGKA2 [DX3021]
uPD78F1840GK [DX3021]
uPD78F1840GKA [DX3021]
uPD78F1840GKA2 [DX3021]
uPD78F1841AGK [DX3021]
uPD78F1841AGKA [DX3021]
uPD78F1841AGKA2 [DX3021]
uPD78F1841GK [DX3021]
uPD78F1841GKA [DX3021]
uPD78F1841GKA2 [DX3021]
uPD78F1842AGK [DX3021]
uPD78F1842AGKA [DX3021]
uPD78F1842AGKA2 [DX3021]
uPD78F1842GK [DX3021]
uPD78F1842GKA [DX3021]
uPD78F1842GKA2 [DX3021]
uPD78F1843AGK [DX3021]
uPD78F1843AGKA [DX3021]
uPD78F1843AGKA2 [DX3021]
uPD78F1843GK [DX3021]
uPD78F1843GKA [DX3021]
uPD78F1843GKA2 [DX3021]
uPD78F1844AGK [DX3021]
uPD78F1844AGKA [DX3021]
uPD78F1844AGKA2 [DX3021]
uPD78F1844GK [DX3021]
uPD78F1844GKA [DX3021]
uPD78F1844GKA2 [DX3021]
uPD78F1845AGK [DX3021]
uPD78F1845AGKA [DX3021]
uPD78F1845AGKA2 [DX3021]
uPD78F1845GK [DX3021]
uPD78F1845GKA [DX3021]
uPD78F1845GKA2 [DX3021]
uPD78F9025@SDIP42 [DX0042]
uPD78F9025@TQFP44 [DX3002]
uPD78F9025A@SDIP42 [DX0042]
uPD78F9025A@TQFP44 [DX3002]
uPD78F9025B@SDIP42 [DX0042]
uPD78F9025B@TQFP44 [DX3002]
uPD78F9026@SDIP42 [DX0042]
uPD78F9026@TQFP44 [DX3002]
uPD78F9026A@SDIP42 [DX0042]
uPD78F9026A@TQFP44 [DX3002]
uPD78F9026B@SDIP42 [DX0042]
uPD78F9026B@TQFP44 [DX3002]
uPD78F9045@SDIP42 [DX0042]
uPD78F9045@TQFP44 [DX3002]
uPD78F9045A@SDIP42 [DX0042]
uPD78F9045A@TQFP44 [DX3002]
uPD78F9045B@SDIP42 [DX0042]
uPD78F9045B@TQFP44 [DX3002]
uPD78F9046@SDIP42 [DX0042]
uPD78F9046@TQFP44 [DX3002]
uPD78F9046A@SDIP42 [DX0042]
uPD78F9046A@TQFP44 [DX3002]
uPD78F9046B@SDIP42 [DX0042]
uPD78F9046B@TQFP44 [DX3002]
uPD78F9076@SSOP30 [DX1027]
uPD78F9076A@SSOP30 [DX1027]
uPD78F9076AMC@SSOP30 [DX1027]
uPD78F9076MC@SSOP30 [DX1027]
uPD78F9116 [DX0001]
uPD78F9116@SSOP30 [DX1027]
uPD78F9116A [DX0001]
uPD78F9116A@SSOP30 [DX1027]
uPD78F9116B [DX0001]
uPD78F9116B@SSOP30 [DX1027]
uPD78F9136 [DX0001]
uPD78F9136@SSOP30 [DX1027]
uPD78F9136A [DX0001]
uPD78F9136A@SSOP30 [DX1027]
uPD78F9136B [DX0001]
uPD78F9136B@SSOP30 [DX1027]
uPD78F9177@LQFP44 [DX3005]
uPD78F9177@QFP48 [DX3007]
uPD78F9177@SDIP42 [DX0042]
uPD78F9177A@LQFP44 [DX3005]

uPD78F9177A@QFP48 [DX3007]
uPD78F9177A@SDIP42 [DX0042]
uPD78F9177AY@LQFP44 [DX3005]
uPD78F9177AY@QFP48 [DX3007]
uPD78F9177AY@SDIP42 [DX0042]
uPD78F9177C@LQFP44 [DX3005]
uPD78F9177C@QFP48 [DX3007]
uPD78F9177C@SDIP42 [DX0042]
uPD78F9177Y@LQFP44 [DX3005]
uPD78F9177Y@QFP48 [DX3007]
uPD78F9177Y@SDIP42 [DX0042]
uPD78F9189@SDIP32 [DX0032]
uPD78F9189CT@SDIP32 [DX0032]
uPD78F9200(A)@SSOP10 [DX1000]
uPD78F9200(A2)@SSOP10 [DX1000]
uPD78F9200@SSOP10 [DX1000]
uPD78F9201(A)@SSOP10 [DX1000]
uPD78F9201(A2)@SSOP10 [DX1000]
uPD78F9201@SSOP10 [DX1000]
uPD78F9202(A)@SSOP10 [DX1000]
uPD78F9202(A2)@SSOP10 [DX1000]
uPD78F9202@SSOP10 [DX1000]
uPD78F9210(A)@SSOP16 [DX1000]
uPD78F9210(A2)@SSOP16 [DX1000]
uPD78F9210@SSOP16 [DX1000]
uPD78F9211(A)@SSOP16 [DX1000]
uPD78F9211(A2)@SSOP16 [DX1000]
uPD78F9211@SSOP16 [DX1000]
uPD78F9212(A)@SSOP16 [DX1000]
uPD78F9212(A2)@SSOP16 [DX1000]
uPD78F9212@SSOP16 [DX1000]
uPD78F9221(A)@SSOP20 [DX1074]
uPD78F9221(A2)@SSOP20 [DX1074]
uPD78F9221@SSOP20 [DX1074]
uPD78F9222(A)@SSOP20 [DX1074]
uPD78F9222(A2)@SSOP20 [DX1074]
uPD78F9222@SSOP20 [DX1074]
uPD78F9224(A)@SSOP20 [DX1074]
uPD78F9224(A2)@SSOP20 [DX1074]
uPD78F9224@SSOP20 [DX1074]
uPD78F9232(A)@SDIP32 [DX0032]
uPD78F9232(A)@SSOP30 [DX1027]
uPD78F9232(A2)@SDIP32 [DX0032]
uPD78F9232(A2)@SSOP30 [DX1027]
uPD78F9232@SDIP32 [DX0032]
uPD78F9232@SSOP30 [DX1027]
uPD78F9234(A)@SDIP32 [DX0032]
uPD78F9234(A)@SSOP30 [DX1027]
uPD78F9234(A2)@SDIP32 [DX0032]
uPD78F9234(A2)@SSOP30 [DX1027]
uPD78F9234@SDIP32 [DX0032]
uPD78F9234@SSOP30 [DX1027]
uPD78F9328GB [DX3010]
uPD78F9500(A)@SSOP10 [DX1000]
uPD78F9500(A2)@SSOP10 [DX1000]
uPD78F9500@SSOP10 [DX1000]
uPD78F9501(A)@SSOP10 [DX1000]
uPD78F9501(A2)@SSOP10 [DX1000]
uPD78F9501@SSOP10 [DX1000]
uPD78F9502(A)@SSOP10 [DX1000]
uPD78F9502(A2)@SSOP10 [DX1000]
uPD78F9502@SSOP10 [DX1000]
uPD78F9510(A)@SSOP16 [DX1000]
uPD78F9510(A2)@SSOP16 [DX1000]
uPD78F9510@SSOP16 [DX1000]
uPD78F9511(A)@SSOP16 [DX1000]
uPD78F9511(A2)@SSOP16 [DX1000]
uPD78F9511@SSOP16 [DX1000]
uPD78F9512(A)@SSOP16 [DX1000]
uPD78F9512(A2)@SSOP16 [DX1000]
uPD78F9512@SSOP16 [DX1000]
uPD78F9521(A)@SSOP20 [DX1074]
uPD78F9521(A2)@SSOP20 [DX1074]
uPD78F9521@SSOP20 [DX1074]
uPD78F9522(A)@SSOP20 [DX1074]
uPD78F9522(A2)@SSOP20 [DX1074]
uPD78F9522@SSOP20 [DX1074]
uPD78F9524(A)@SSOP20 [DX1074]
uPD78F9524(A2)@SSOP20 [DX1074]
uPD78F9524@SSOP20 [DX1074]
uPD78F9532(A)@SDIP32 [DX0032]
uPD78F9532(A)@SSOP30 [DX1027]
uPD78F9532(A2)@SDIP32 [DX0032]
uPD78F9532(A2)@SSOP30 [DX1027]
uPD78F9532@SDIP32 [DX0032]
uPD78F9532@SSOP30 [DX1027]
uPD78F9534(A)@SDIP32 [DX0032]
uPD78F9534(A)@SSOP30 [DX1027]
uPD78F9534(A2)@SDIP32 [DX0032]
uPD78F9534(A2)@SSOP30 [DX1027]
uPD78F9534@SDIP32 [DX0032]
uPD78F9534@SSOP30 [DX1027]
uPD78P054FGC@QFP80 [DX3018]
uPD78P054FGK@TQFP80 [DX3016]
uPD78P054GC@QFP80 [DX3018]
uPD78P054GK@TQFP80 [DX3016]

uPD78P054YGC@QFP80 [DX3018]
uPD78P058FGC@QFP80 [DX3018]
uPD78P058GC@QFP80 [DX3018]
uPD78P058YGC@QFP80 [DX3018]
uPD78P064G@QFP100 [DX3022]
uPD78P064GF@QFP100 [DX3022]
uPD78P083@TQFP44 [DX3002]
uPD78P083A@TQFP44 [DX3002]
uPD78P083B@TQFP44 [DX3002]
uPD78P214L [DX2168]
uPD78P218L [DX2168]
uPD78P312ADW [DX0064]
uPD78P312AGQ [DX0064]
uPD78P312AR [DX0064]
uPD78P312DW [DX0064]
uPD78P312GQ [DX0064]
uPD78P312R [DX0064]
uPD78P40368GC@QFP80 [DX3018]
uPD78P4036GK@TQFP80 [DX3016]
uPD78P4036YGC@QFP80 [DX3018]
uPD78P4036YGK@TQFP80 [DX3016]
uPD78P4038GC@QFP80 [DX3018]
uPD78P4038GK@TQFP80 [DX3016]
uPD78P4038YGC@QFP80 [DX3018]
uPD78P4038YGK@TQFP80 [DX3016]
uPD78P9014CT@SDIP28 [DX0032]
uPD79F7020CT [DX0032]
uPD79F7020GB [DX3010]
uPD79F7021CTA [DX0032]
uPD79F7022CTA [DX0032]
uPD79F7023CTA [DX0032]
UPD79F7024MC [DX1074]
UPD79F7026@QFP32 [DX3001]
uPD79F8200(A2)@SSOP10 [DX1000]
uPD79F8201(A)@SSOP10 [DX1000]
uPD79F8201@SSOP10 [DX1000]
uPD79F8202(A2)@SSOP10 [DX1000]
uPD79F8210(A)@SSOP16 [DX1000]
uPD79F8210@SSOP16 [DX1000]
uPD79F8211(A2)@SSOP16 [DX1000]
uPD79F8212(A)@SSOP16 [DX1000]
uPD79F8212@SSOP16 [DX1000]
uPD79F8221(A2)@SSOP20 [DX1074]
uPD79F8222(A)@SSOP20 [DX1074]
uPD79F8222@SSOP20 [DX1074]
uPD79F8224(A2)@SSOP20 [DX1074]
uPD79F8232(A)@SDIP32 [DX0032]
uPD79F8232(A2)@SDIP32 [DX0032]
uPD78P054YGK@TQFP80 [DX3016]
uPD78P058FGK@TQFP80 [DX3016]
uPD78P058GK@TQFP80 [DX3016]
uPD78P058YGK@TQFP80 [DX3016]
uPD78P064GC@LQFP100 [DX3021]
uPD78P083@SDIP42 [DX0042]
uPD78P083A@SDIP42 [DX0042]
uPD78P083B@SDIP42 [DX0042]
uPD78P214CW@SDIP64 [DX0064]
uPD78P218CW [DX0064]
uPD78P312ACW [DX0064]
uPD78P312AGF [DX0064]
uPD78P312AL [DX0064]
uPD78P312CW [DX0064]
uPD78P312GF [DX0064]
uPD78P312L [DX0064]
uPD78P368AGF [DX3019]
uPD78P4036GC-A@QFP80 [DX3018]
uPD78P4036GK-A@TQFP80 [DX3016]
uPD78P4036YGC-A@QFP80 [DX3018]
uPD78P4036YGK-A@TQFP80 [DX3016]
uPD78P4038GC-A@QFP80 [DX3018]
uPD78P4038GK-A@TQFP80 [DX3016]
uPD78P4038YGC-A@QFP80 [DX3018]
uPD78P4038YGK-A@TQFP80 [DX3016]
uPD78P9014GT@SOIC28 [DX1033]
uPD79F7020CTA [DX0032]
uPD79F7021CT [DX0032]
uPD79F7022CT [DX0032]
uPD79F7023CT [DX0032]
UPD79F7023MC [DX1074]
UPD79F7025@QFP32 [DX3001]
uPD79F8200(A)@SSOP10 [DX1000]
uPD79F8200@SSOP10 [DX1000]
uPD79F8201(A2)@SSOP10 [DX1000]
uPD79F8202(A)@SSOP10 [DX1000]
uPD79F8202@SSOP10 [DX1000]
uPD79F8210(A2)@SSOP16 [DX1000]
uPD79F8211(A)@SSOP16 [DX1000]
uPD79F8211@SSOP16 [DX1000]
uPD79F8212(A2)@SSOP16 [DX1000]
uPD79F8221(A)@SSOP20 [DX1074]
uPD79F8221@SSOP20 [DX1074]
uPD79F8222(A2)@SSOP20 [DX1074]
uPD79F8224(A)@SSOP20 [DX1074]
uPD79F8224@SSOP20 [DX1074]
uPD79F8232(A)@SSOP30 [DX1027]
uPD79F8232(A2)@SSOP30 [DX1027]

uPD79F8232@SDIP32 [DX0032]
uPD79F8234(A)@SDIP32 [DX0032]
uPD79F8234(A2)@SDIP32 [DX0032]
uPD79F8234@SDIP32 [DX0032]
uPD79F8430GB@QFP52 [DX3010]
uPD79F8432GB@QFP52 [DX3010]
uPD79F8434GB@QFP52 [DX3010]
uPD79F8452GB [DX3011]
uPD79F8453GB [DX3011]
uPD79F8454GB [DX3011]
uPD79F8455GB [DX3011]
uPD79F8456GB [DX3011]
uPD79F8457GB [DX3011]
uPD79F8500(A)@SSOP10 [DX1000]
uPD79F8500@SSOP10 [DX1000]
uPD79F8501(A2)@SSOP10 [DX1000]
uPD79F8502(A)@SSOP10 [DX1000]
uPD79F8502@SSOP10 [DX1000]
uPD79F8510(A2)@SSOP16 [DX1000]
uPD79F8511(A)@SSOP16 [DX1000]
uPD79F8511@SSOP16 [DX1000]
uPD79F8511AGB@QFP44 [DX3005]
uPD79F8511GA@QFP48 [DX3047]
uPD79F8511MC@SSOP38 [DX1027]
uPD79F8512(A2)@SSOP16 [DX1000]
uPD79F8512AGA@QFP48 [DX3047]
uPD79F8512AMC@SSOP38 [DX1027]
uPD79F8512GB@QFP44 [DX3005]
uPD79F8513AGA@QFP48 [DX3047]
uPD79F8513AMC@SSOP38 [DX1027]
uPD79F8513GB@QFP44 [DX3005]
uPD79F8514AGA@QFP48 [DX3047]
uPD79F8514AMC@SSOP38 [DX1027]
uPD79F8514GB@QFP44 [DX3005]
uPD79F8515AGA@QFP48 [DX3047]
uPD79F8515AMC@SSOP38 [DX1027]
uPD79F8515GB@QFP44 [DX3005]
uPD79F8521(A)@SSOP20 [DX1074]
uPD79F8521@SSOP20 [DX1074]
uPD79F8522(A2)@SSOP20 [DX1074]
uPD79F8524(A)@SSOP20 [DX1074]
uPD79F8524@SSOP20 [DX1074]
uPD79F8525AGBA [DX3010]
uPD79F8525GB [DX3010]
uPD79F8525GBA2 [DX3010]
uPD79F8532(A)@SSOP30 [DX1027]
uPD79F8532(A2)@SSOP30 [DX1027]
uPD79F8532@SSOP30 [DX1027]
uPD79F8232@SSOP30 [DX1027]
uPD79F8234(A)@SSOP30 [DX1027]
uPD79F8234(A2)@SSOP30 [DX1027]
uPD79F8234@SSOP30 [DX1027]
uPD79F8431GB@QFP52 [DX3010]
uPD79F8433GB@QFP52 [DX3010]
uPD79F8435GB@QFP52 [DX3010]
uPD79F8452GK [DX3012]
uPD79F8453GK [DX3012]
uPD79F8454GK [DX3012]
uPD79F8455GK [DX3012]
uPD79F8456GK [DX3012]
uPD79F8457GK [DX3012]
uPD79F8500(A2)@SSOP10 [DX1000]
uPD79F8501(A)@SSOP10 [DX1000]
uPD79F8501@SSOP10 [DX1000]
uPD79F8502(A2)@SSOP10 [DX1000]
uPD79F8510(A)@SSOP16 [DX1000]
uPD79F8510@SSOP16 [DX1000]
uPD79F8511(A2)@SSOP16 [DX1000]
uPD79F8511AGA@QFP48 [DX3047]
uPD79F8511AMC@SSOP38 [DX1027]
uPD79F8511GB@QFP44 [DX3005]
uPD79F8512(A)@SSOP16 [DX1000]
uPD79F8512@SSOP16 [DX1000]
uPD79F8512AGB@QFP44 [DX3005]
uPD79F8512GA@QFP48 [DX3047]
uPD79F8512MC@SSOP38 [DX1027]
uPD79F8513AGB@QFP44 [DX3005]
uPD79F8513GA@QFP48 [DX3047]
uPD79F8513MC@SSOP38 [DX1027]
uPD79F8514AGB@QFP44 [DX3005]
uPD79F8514GA@QFP48 [DX3047]
uPD79F8514MC@SSOP38 [DX1027]
uPD79F8515AGB@QFP44 [DX3005]
uPD79F8515GA@QFP48 [DX3047]
uPD79F8515MC@SSOP38 [DX1027]
uPD79F8521(A2)@SSOP20 [DX1074]
uPD79F8522(A)@SSOP20 [DX1074]
uPD79F8522@SSOP20 [DX1074]
uPD79F8524(A2)@SSOP20 [DX1074]
uPD79F8525AGB [DX3010]
uPD79F8525AGBA2 [DX3010]
uPD79F8525GBA [DX3010]
uPD79F8532(A)@SDIP32 [DX0032]
uPD79F8532(A2)@SDIP32 [DX0032]
uPD79F8532@SDIP32 [DX0032]
uPD79F8534(A)@SDIP32 [DX0032]

uPD79F8534(A)@SSOP30 [DX1027]
uPD79F8534(A2)@SSOP30 [DX1027]
uPD79F8534@SSOP30 [DX1027]
uPD79F9203MC [DX1027]
uPD79F9205MC [DX1027]
uPD79F9211GB [DX3003]
uPD79F9213GA [DX3007]
uPD79F9213MC [DX1027]
uPD79F9214GB [DX3003]
uPD79F9215GA [DX3007]
uPD79F9215MC [DX1027]
uPD79F9223GB [DX3009]
uPD79F9225GB [DX3009]
uPD79F9231GK [DX3064]
uPD79F9233GK [DX3064]
uPD79F9234GK [DX3064]
uPD79F9235GK [DX3064]
uPD8748 [DX0001]
uPD8748HD [DX0001]
uPD8749HD [DX0001]
uPD79F8534(A2)@SDIP32 [DX0032]
uPD79F8534@SDIP32 [DX0032]
uPD79F9201MC [DX1027]
uPD79F9204MC [DX1027]
uPD79F9211GA [DX3007]
uPD79F9211MC [DX1027]
uPD79F9213GB [DX3003]
uPD79F9214GA [DX3007]
uPD79F9214MC [DX1027]
uPD79F9215GB [DX3003]
uPD79F9221GB [DX3009]
uPD79F9224GB [DX3009]
uPD79F9231GB [DX3011]
uPD79F9233GB [DX3011]
uPD79F9234GB [DX3011]
uPD79F9235GB [DX3011]
uPD8741A [DX0001]
uPD8748H [DX0001]
uPD8749H [DX0001]

NEXFLASH

E(E)PROM/FRAM/NVRAM

NX25B40(Bottom Boot)@MLP8 [DX4005#1]
NX25B40(Bottom Boot)@SOIC8 [DX1045#1]
NX25B40(Top Boot)@MLP8 [DX4005#1]
NX25B40(Top Boot)@SOIC8 [DX1045#1]
NX25P10@MLP8 [DX4005]
NX25P16@MLP8 [DX4005#1]
NX25P16@SOIC16 [DX1072#1]
NX25P16@SOIC8 [DX1044#1]
NX25P20@MLP8 [DX4005#1]
NX25P32@MLP8 [DX1044#1]
NX25P32@SOIC16 [DX1072#1]
NX25P40@MLP8 [DX4005#1]
NX25P64@MLP8 [DX4005#1]
NX25P64@SOIC16 [DX1072#1]
NX25P80@MLP8 [DX4005#1]
NX29F010 [DX0001]
NX29F010@TSOP32 [DX1002]
NX25P10@SOIC8 [DX1045]
NX25P16@MLP8(ISP) [DX0001]
NX25P16@SOIC16(ISP) [DX0001]
NX25P16@SOIC8(ISP) [DX0001]
NX25P20@SOIC8 [DX1045#1]
NX25P32@MLP8(ISP) [DX0001]
NX25P32@SOIC16(ISP) [DX0001]
NX25P40@SOIC8 [DX1045#1]
NX25P64@MLP8(ISP) [DX0001]
NX25P64@SOIC16(ISP) [DX0001]
NX25P80@SOIC8 [DX1045#1]
NX29F010@PLCC32 [DX2032]

NJRC

E(E)PROM/FRAM/NVRAM

NJU26040V [DX0001]
NJU26040V@SSOP32 [DX1026]

NORDIC

MICROCONTROLLER

NRF24LE1@QFN24 [DX4012]
NRF24LE1@QFN32 [DX4015-6]
NRF24LE1@QFN48 [DX4021]
NRF24LE1D@QFN24 [DX4012]
NRF24LE1E@QFN32 [DX4015-6]
NRF24LE1E@QFN32(fullrich) [DX4015-7]
NRF24LE1F@QFN48 [DX4021]
NRF24LE1-F16@QFN24 [DX4012]
NRF24LE1-F16@QFN32 [DX4015-6]
NRF24LE1-F16@QFN48 [DX4021]
NRF24LE1G@QFN32 [DX4015-6]
NRF24LE1H@QFN48 [DX4021]
NRF24LE1I@QFN24 [DX4012]
NRF24LE1-O17@QFN24 [DX4012]
NRF24LE1-O17@QFN32 [DX4015-6]
NRF24LE1-O17@QFN32(fullrich) [DX4015-7]
NRF24LE1-O17@QFN32(TECHEN) [DX4015-6]
NRF24LE1-O17@QFN48 [DX4021]
NRF24LU1@QFN32 [DX4015-6]
NRF24LU1-F16@QFN32 [DX4015-6]
NRF24LU1P@QFN32 [DX4015-6]
NRF24LU1P-F16@QFN32 [DX4015-6]
NRF24LU1P-F32@QFN32 [DX4015-6]
NRF24LU1P-O17@QFN32 [DX4015-6]
nRF31512@QFN28 [DX4033]
nRF31512@QFN32 [DX4015]
nRF31512C@QFN28 [DX4033]
nRF31512C@QFN32 [DX4015]
nRF31562@QFN24 [DX4012]
nRF31562A@QFN24 [DX4012]
NRFLU1P16@QFN32 [DX4015-6]

NOVATEK

MICROCONTROLLER

NT68F631@PLCC44 [DX2044]
NT68F631@SDIP42 [DX0042]
NT68F631ALG@PLCC44 [DX2044]
NT68F631AUG@SDIP42 [DX0042]
NT68F631L@PLCC44 [DX2044]
NT68F631LG@PLCC44 [DX2044]
NT68F631U@SDIP42 [DX0042]
NT68F631UG@SDIP42 [DX0042]
NT68F632@PLCC44 [DX2044]
NT68F632@SDIP42 [DX0042]
NT68F632ALG@PLCC44 [DX2044]
NT68F632AUG@SDIP42 [DX0042]
NT68F632L@PLCC44 [DX2044]
NT68F632LG@PLCC44 [DX2044]
NT68F632U@SDIP42 [DX0042]
NT68F632UG@SDIP42 [DX0042]
NT68F633@PLCC44 [DX2044]
NT68F633@SDIP42 [DX0042]
NT68F633L@PLCC44 [DX2044]
NT68F633LG@PLCC44 [DX2044]
NT68F633U@SDIP42 [DX0042]
NT68F633UG@SDIP42 [DX0042]
NT68F636@PLCC44 [DX2044]
NT68F636@SDIP42 [DX0042]
NT68F636L@PLCC44 [DX2044]
NT68F636LG@PLCC44 [DX2044]
NT68F636U@SDIP42 [DX0042]
NT68F636UG@SDIP42 [DX0042]
NT68F63L(0444)@PLCC44 [DX2044]
NT68F63L(0444)@SDIP42 [DX0042]
NT68F63L(0448)@PLCC44 [DX2044]
NT68F63L(0448)@SDIP42 [DX0042]

NT68F63L(0523)@PLCC44 [DX2044]
NT68F63L(0523)@SDIP42 [DX0042]
NT68F63L@PLCC44 [DX2044]
NT68F63LA@PLCC44 [DX2044]
NT68F63LG@PLCC44 [DX2044]
NT68F63LGG@PLCC44 [DX2044]
NT68F63U@SDIP42 [DX0042]
NT68F63UA@SDIP42 [DX0042]
NT68F63UG@SDIP42 [DX0042]
NT68F63UGG@SDIP42 [DX0042]

NSC

E(E)PROM/FRAM/NVRAM

2864 [DX0001]
MM2716 [DX0001]
MM2716E [DX0001]
NM24C02 [DX0001]
NM24C02@SOIC8 [DX1045]
NM24C02@TSOP8 [DX1059]
NM24C02L [DX0001]
NM24C02L@SOIC8 [DX1045]
NM24C02L@TSOP8 [DX1059]
NM24C03 [DX0001]
NM24C03@SOIC8 [DX1045]
NM24C03@TSOP8 [DX1059]
NM24C04 [DX0001]
NM24C04@SOIC8 [DX1045]
NM24C04@TSOP8 [DX1059]
NM24C05 [DX0001]
NM24C05@SOIC8 [DX1045]
NM24C05@TSOP8 [DX1059]
NM24C08 [DX0001]
NM24C08@SOIC8 [DX1045]
NM24C09 [DX0001]
NM24C09@SOIC8 [DX1045]
NM24C16 [DX0001]
NM24C16@SOIC8 [DX1045]
NM24C17 [DX0001]
NM24C17@SOIC8 [DX1045]
NM27C010 [DX0001]
NM27C010@PLCC32 [DX2032]
NM27C010@TSOP32 [DX1002]
NM27C010Q [DX0001]
NM27C010Q@PLCC32 [DX2032]
NM27C010Q@TSOP32 [DX1002]
NM27C020 [DX0001]
NM27C020@PLCC32 [DX2032]
NM27C020@TSOP32 [DX1002]
NM27C020Q [DX0001]
NM27C020Q@PLCC32 [DX2032]
NM27C020Q@TSOP32 [DX1002]
NM27C040 [DX0001]
NM27C040@PLCC32 [DX2032]
NM27C040@TSOP32 [DX1002]
NM27C1023 [DX0001]
NM27C128 [DX0001]
NM27C128@PLCC32 [DX2032]
NM27C210 [DX0001]
NM27C210@PLCC44 [DX2044]
NM27C210Q [DX0001]
NM27C210Q@PLCC44 [DX2044]
NM27C240 [DX0001]
NM27C240@PLCC44 [DX2044]
NM27C256 [DX0001]
NM27C256@PLCC32 [DX2032]
NM27C400 [DX0001]
NM27C512 [DX0001]
NM27C512@PLCC32 [DX2032]
NM27C512Q [DX0001]
NM27C512Q@PLCC32 [DX2032]
NM27C64Q [DX0001]
NM27C64Q@PLCC32 [DX2032]
NM27CP256 [DX0001]
NM27CP256@PLCC32 [DX2032]
NM27LC010 [DX0001]
NM27LC010@PLCC32 [DX2032]
NM27LC010@TSOP32 [DX1002]
NM27LC256 [DX0001]
NM27LC256@PLCC32 [DX2032]
NM27LC512 [DX0001]
NM27LC512@PLCC32 [DX2032]
NM27LC64 [DX0001]
NM27LC64@PLCC32 [DX2032]
NM27LV010 [DX0001]
NM27LV010@PLCC32 [DX2032]
NM27LV010@TSOP32 [DX1002]
NM27LV210 [DX0001]

NM27LV210@PLCC44 [DX2044]
NM27LV512@PLCC32 [DX2032]
NM27P040 [DX0001]
NM27P040@TSOP32 [DX1002]
NM27P210@PLCC44 [DX2044]
NM27P512@PLCC32 [DX2032]
NM59C11@SOIC8 [DX1045]
NM93C06(08bit)@SOIC8 [DX1045]
NM93C06(16bit)@SOIC8 [DX1045]
NM93C46@SOIC8 [DX1045]
NM93C46A(08bit)@SOIC8 [DX1045]
NM93C46A(16bit)@SOIC8 [DX1045]
NM93C46AL(08bit)@SOIC8 [DX1045]
NM93C46AL(16bit)@SOIC8 [DX1045]
NM93C46ALZ(08bit)@SOIC8 [DX1045]
NM93C46ALZ(16bit)@SOIC8 [DX1045]
NM93C46L@SOIC8 [DX1045]
NM93C46LZ@SOIC8 [DX1045]
NM93C56@SOIC8 [DX1045]
NM93C56A(08bit)@SOIC8 [DX1045]
NM93C56A(16bit)@SOIC8 [DX1045]
NM93C56AL(08bit)@SOIC8 [DX1045]
NM93C56AL(16bit)@SOIC8 [DX1045]
NM93C56ALZ(08bit)@SOIC8 [DX1045]
NM93C56ALZ(16bit)@SOIC8 [DX1045]
NM93C56L@SOIC8 [DX1045]
NM93C56LZ@SOIC8 [DX1045]
NM93C66@SOIC8 [DX1045]
NM93C66A(08bit) [DX0001]
NM93C66A@SOIC8 [DX1045]
NM93C66AL(08bit)@SOIC8 [DX1045]
NM93C66AL(16bit)@SOIC8 [DX1045]
NM93C66ALZ(08bit)@SOIC8 [DX1045]
NM93C66ALZ(16bit)@SOIC8 [DX1045]
NM93C66L@SOIC8 [DX1045]
NM93C66LZ@SOIC8 [DX1045]
NM93C86(16bit)@SOIC8 [DX1045]
NM93C86A(08bit) [DX0001]
NM93C86A@SOIC8 [DX1045]
NM93C86AL(08bit)@SOIC8 [DX1045]
NM93C86AL(16bit)@SOIC8 [DX1045]
NM93C86ALZ(08bit)@SOIC8 [DX1045]
NM93C86ALZ(16bit)@SOIC8 [DX1045]
NM93C86L@SOIC8 [DX1045]
NM93C86LZ@SOIC8 [DX1045]
NM93CS06(MT8)@TSSOP8 [DX1059]
NM93CS46(M8)@SOIC8 [DX1045]
NM93CS46(N) [DX0001]
NM27LV512 [DX0001]
NM27LV512@TSOP32 [DX1002]
NM27P040@PLCC32 [DX2032]
NM27P210 [DX0001]
NM27P512 [DX0001]
NM59C11 [DX0001]
NM93C06(08bit) [DX0001]
NM93C06(16bit) [DX0001]
NM93C46 [DX0001]
NM93C46A(08bit) [DX0001]
NM93C46A(16bit) [DX0001]
NM93C46AL(08bit) [DX0001]
NM93C46AL(16bit) [DX0001]
NM93C46ALZ(08bit) [DX0001]
NM93C46ALZ(16bit) [DX0001]
NM93C46L [DX0001]
NM93C46LZ [DX0001]
NM93C56 [DX0001]
NM93C56A(08bit) [DX0001]
NM93C56A(16bit) [DX0001]
NM93C56AL(08bit) [DX0001]
NM93C56AL(16bit) [DX0001]
NM93C56ALZ(08bit) [DX0001]
NM93C56ALZ(16bit) [DX0001]
NM93C56L [DX0001]
NM93C56LZ [DX0001]
NM93C66 [DX0001]
NM93C66A [DX0001]
NM93C66A(08bit)@SOIC8 [DX1045]
NM93C66AL(08bit) [DX0001]
NM93C66AL(16bit) [DX0001]
NM93C66ALZ(08bit) [DX0001]
NM93C66ALZ(16bit) [DX0001]
NM93C66L [DX0001]
NM93C66LZ [DX0001]
NM93C86(16bit) [DX0001]
NM93C86A [DX0001]
NM93C86A(08bit)@SOIC8 [DX1045]
NM93C86AL(08bit) [DX0001]
NM93C86AL(16bit) [DX0001]
NM93C86ALZ(08bit) [DX0001]
NM93C86ALZ(16bit) [DX0001]
NM93C86L [DX0001]
NM93C86LZ [DX0001]
NM93CS06(M8)@SOIC8 [DX1045]
NM93CS06(N) [DX0001]
NM93CS46(MT8)@TSSOP8 [DX1059]
NM93CS56(M8)@SOIC8 [DX1045]

NM93CS56(MT8)@TSSOP8 [DX1059]
NM93CS66(M8)@SOIC8 [DX1045]
NM93CS66(N) [DX0001]
NMC2732B [DX0001]
NMC27C010 [DX0001]
NMC27C010@TSOP32 [DX1002]
NMC27C1024@PLCC44 [DX2044]
NMC27C128B@PLCC32 [DX2032]
NMC27C128BN@PLCC32 [DX2032]
NMC27C128BQ@PLCC32 [DX2032]
NMC27C128Q [DX0001]
NMC27C16BQ [DX0001]
NMC27C16H [DX0001]
NMC27C16Q [DX0001]
NMC27C210@PLCC44 [DX2044]
NMC27C210Q@PLCC44 [DX2044]
NMC27C256B@PLCC32 [DX2032]
NMC27C256BQE [DX0001]
NMC27C256Q [DX0001]
NMC27C32 [DX0001]
NMC27C32BQ [DX0001]
NMC27C32EH [DX0001]
NMC27C512 [DX0001]
NMC27C512A [DX0001]
NMC27C512AN [DX0001]
NMC27C64 [DX0001]
NMC27C64BN [DX0001]
NMC27CP128 [DX0001]
NMC27CP64 [DX0001]
NMC59C11@SOIC8 [DX1045]
NMC87C257Q@PLCC32 [DX2032]
NMC87C257V@PLCC32 [DX2032]
NMC9306@SOIC8 [DX1045]
NMC9307@SOIC8 [DX1045]
NMC9346@SOIC8 [DX1045]
NMC93C56@SOIC14 [DX1016]
NMC93C66 [DX0001]
NMC93C86A [DX0001]
NMC93C86A@SOIC8 [DX1045]
NMC93CS06(N) [DX0001]
NMC93CS46(N) [DX0001]
NMC93CS56(N) [DX0001]
NMC93CS66(N) [DX0001]
NMC93S06(N) [DX0001]
NMC9817A [DX0001]
NS9816A [DX0001]
NM93CS56(N) [DX0001]
NM93CS66(MT8)@TSSOP8 [DX1059]
NMC2732 [DX0001]
NMC2732H [DX0001]
NMC27C010@PLCC32 [DX2032]
NMC27C1024 [DX0001]
NMC27C128B [DX0001]
NMC27C128BN [DX0001]
NMC27C128BQ [DX0001]
NMC27C128CQ [DX0001]
NMC27C16 [DX0001]
NMC27C16BQE [DX0001]
NMC27C16HQ [DX0001]
NMC27C210 [DX0001]
NMC27C210Q [DX0001]
NMC27C256B [DX0001]
NMC27C256BN [DX0001]
NMC27C256BQM [DX0001]
NMC27C256Q@PLCC32 [DX2032]
NMC27C32B [DX0001]
NMC27C32E [DX0001]
NMC27C32H [DX0001]
NMC27C512@PLCC32 [DX2032]
NMC27C512A@PLCC32 [DX2032]
NMC27C512AN@PLCC32 [DX2032]
NMC27C64@PLCC32 [DX2032]
NMC27C64N [DX0001]
NMC27CP256 [DX0001]
NMC59C11 [DX0001]
NMC87C257Q [DX0001]
NMC87C257V [DX0001]
NMC9306 [DX0001]
NMC9307 [DX0001]
NMC9346 [DX0001]
NMC93C56 [DX0001]
NMC93C56@SOIC8 [DX1045]
NMC93C66@SOIC14 [DX1016]
NMC93C86A@SOIC14 [DX1016]
NMC93CS06(M14)@SOIC14 [DX1016]
NMC93CS46(M14)@SOIC14 [DX1016]
NMC93CS56(M14)@SOIC14 [DX1016]
NMC93CS66(M14)@SOIC14 [DX1016]
NMC93S06(M14)@SOIC14 [DX1016]
NMC9817 [DX0001]
NS2816A [DX0001]

BPROM

DM54LS471 [DX0001]
DM54LS471@PLCC20 [DX2020]
DM54S188 [DX0001]
DM54S188A [DX0001]
DM54S287 [DX0001]
DM54S287A [DX0001]
DM54S288 [DX0001]
DM54S288A [DX0001]
DM54S387 [DX0001]
DM54S387A [DX0001]
DM54S471 [DX0001]
DM54S471@PLCC20 [DX2020]
DM54S472 [DX0001]
DM54S472@PLCC20 [DX2020]
DM54S472A [DX0001]
DM54S472A@PLCC20 [DX2020]
DM54S472B [DX0001]
DM54S472B@PLCC20 [DX2020]
DM54S473 [DX0001]
DM54S473@PLCC20 [DX2020]
DM54S473A [DX0001]
DM54S473A@PLCC20 [DX2020]
DM54S474 [DX0001]
DM54S474A [DX0001]
DM54S474B [DX0001]
DM54S475 [DX0001]
DM54S475A [DX0001]
DM54S570 [DX0001]
DM54S570A [DX0001]
DM54S571 [DX0001]
DM54S571A [DX0001]
DM54S571B [DX0001]
DM54S572 [DX0001]
DM54S572A [DX0001]
DM54S573 [DX0001]
DM54S573A [DX0001]
DM54S573B [DX0001]
DM74LS471 [DX0001]
DM74LS471@PLCC20 [DX2020]
DM74S188 [DX0001]
DM74S188A [DX0001]
DM74S287 [DX0001]
DM74S287A [DX0001]
DM74S288 [DX0001]
DM74S288A [DX0001]
DM74S387 [DX0001]
DM74S387A [DX0001]
DM74S471 [DX0001]
DM74S471@PLCC20 [DX2020]
DM74S472 [DX0001]
DM74S472@PLCC20 [DX2020]
DM74S472A [DX0001]
DM74S472A@PLCC20 [DX2020]
DM74S472B [DX0001]
DM74S472B@PLCC20 [DX2020]
DM74S473 [DX0001]
DM74S473@PLCC20 [DX2020]
DM74S473A [DX0001]
DM74S473A@PLCC20 [DX2020]
DM74S474 [DX0001]
DM74S474A [DX0001]
DM74S474B [DX0001]
DM74S475 [DX0001]
DM74S475A [DX0001]
DM74S570 [DX0001]
DM74S570A [DX0001]
DM74S571 [DX0001]
DM74S571A [DX0001]
DM74S571B [DX0001]
DM74S572 [DX0001]
DM74S572A [DX0001]
DM74S573 [DX0001]
DM74S573A [DX0001]
DM74S573B [DX0001]

PLD

GAL16V8 [DX0001]
GAL16V8@PLCC20 [DX2020]
GAL16V8A [DX0001]
GAL16V8A@PLCC20 [DX2020]
PAL10H8 [DX0001]
PAL10H8A [DX0001]
PAL10H8A2 [DX0001]
PAL10L8 [DX0001]
PAL10L8A [DX0001]
PAL10L8A2 [DX0001]

PAL12H6 [DX0001]
PAL12H6A [DX0001]
PAL12H6A2 [DX0001]
PAL12L6 [DX0001]
PAL12L6A [DX0001]
PAL12L6A2 [DX0001]
PAL14H4 [DX0001]
PAL14H4A [DX0001]
PAL14H4A2 [DX0001]
PAL14L4 [DX0001]
PAL14L4A [DX0001]
PAL14L4A2 [DX0001]
PAL16C1 [DX0001]
PAL16C1A [DX0001]
PAL16C1A2 [DX0001]
PAL16H2 [DX0001]
PAL16H2A [DX0001]
PAL16H2A2 [DX0001]
PAL16L2 [DX0001]
PAL16L2A [DX0001]
PAL16L2A2 [DX0001]
PAL16L8 [DX0001]
PAL16L8A2 [DX0001]
PAL16L8B [DX0001]
PAL16L8B2 [DX0001]
PAL16R4 [DX0001]
PAL16R4A [DX0001]
PAL16R4A2 [DX0001]
PAL16R4B [DX0001]
PAL16R4B2 [DX0001]
PAL16R6 [DX0001]
PAL16R6A [DX0001]
PAL16R6A2 [DX0001]
PAL16R6B [DX0001]
PAL16R6B2 [DX0001]
PAL16R8 [DX0001]
PAL16R8A [DX0001]
PAL16R8A2 [DX0001]
PAL16R8B [DX0001]
PAL16R8B2 [DX0001]

MICROCONTROLLER

COP820(CJMHD) [DX0001]
COP820(CJMHEA)@SOIC28 [DX1033]
COP822(CJMHD) [DX0001]
COP842(CMHD) [DX0001]
COP8640(CMHD) [DX0001]
COP8640(CMHEA)@SOIC28 [DX1033]
COP8642(CMHD) [DX0001]
COP8780(CD) [DX0001]
COP8780(CEL)@PLCC44 [DX2044]
COP8780(CJ) [DX0001]
COP8780(CN) [DX0001]
COP8780(CV)@PLCC44 [DX2044]
COP8781(CD) [DX0001]
COP8781(CJ) [DX0001]
COP8781(CMC)@SOIC28 [DX1033]
COP8781(CN) [DX0001]
COP8781(CWM)@SOIC28 [DX1033]
COP8782(CD) [DX0001]
COP8782(CJ) [DX0001]
COP8782(CMC)@SOIC20 [DX1033]
COP8782(CN) [DX0001]
COP8782(CWM)@SOIC20 [DX1033]
COP8784(CFN) [DX0001]
COP8784(CFWM) [DX0001]
COP8784(CLN) [DX0001]
COP8784(CLWM) [DX0001]
COP8784(EGN) [DX0001]
COP8784(EGWM) [DX0001]
COP8788(CFN) [DX0001]
COP8788(CFV)@PLCC44 [DX2044]
COP8788(CLN) [DX0001]
COP8788(CLV)@PLCC44 [DX2044]
COP8788(EGN) [DX0001]
COP8788(EGV)@PLCC44 [DX2044]
COP87L20 [DX0001]
COP87L20@SOIC28 [DX1033]
COP87L22 [DX0001]
COP87L22@SOIC20 [DX1033]
COP87L40 [DX0001]
COP87L40@SOIC28 [DX1033]
COP87L42 [DX0001]
COP87L42@SOIC20 [DX1033]
COP87L84 [DX0001]
COP87L84@SOIC28 [DX1033]
COP87L84BC [DX0001]
COP87L84BC@SOIC28 [DX1033]
COP87L88 [DX0001]
COP87L88@PLCC44 [DX2044]

COP87L88@PLCC68 [DX2068]
COP87L88EB@PLCC44 [DX2044]
COP87L88GW@PLCC68 [DX2068]
COP880(CMHEL)@PLCC44 [DX2044]
COP881(CMHEA)@SOIC28 [DX1033]
COP884(CFMHEA)@SOIC28 [DX1033]
COP884(CGMHEA)@SOIC28 [DX1033]
COP884(CLMHEA)@SOIC28 [DX1033]
COP884(CSMHEA)@SOIC28 [DX1033]
COP884(EGMHEA)@SOIC28 [DX1033]
COP888(CFMHEL)@PLCC44 [DX2044]
COP888(CGMHEL)@PLCC44 [DX2044]
COP888(CLMHEL)@PLCC44 [DX2044]
COP888(CSMHEL)@PLCC44 [DX2044]
COP888(EGMHEL)@PLCC44 [DX2044]
COP8ACC720@SOIC20 [DX1033]
COP8ACC728@SOIC28 [DX1033]
COP8ALE728@SOIC28 [DX1033]
COP8AXE9@SOIC28 [DX1033]
COP8CBE9@TQFP44 [DX3002]
COP8CBR9@PLCC68 [DX2068]
COP8CCE9@PLCC44 [DX2044]
COP8CCR9@PLCC44 [DX2044]
COP8CCR9@TQFP44 [DX3002]
COP8CDR9@PLCC68 [DX2068]
COP8CXC9@PLCC44 [DX2044]
COP8SAA716 [DX0001]
COP8SAA720 [DX0001]
COP8SAA728 [DX0001]
COP8SAA728@SOIC28 [DX1033]
COP8SAA740@SOIC40 [DX1014]
COP8SAA744@TQFP44 [DX3002]
COP8SAB716@SOIC16 [DX1033]
COP8SAB720@SOIC20 [DX1033]
COP8SAB728@PLCC28 [DX2028]
COP8SAB740 [DX0001]
COP8SAB744@PLCC44 [DX2044]
COP8SAC716 [DX0001]
COP8SAC720 [DX0001]
COP8SAC728 [DX0001]
COP8SAC728@SOIC28 [DX1033]
COP8SAC740@SOIC40 [DX1014]
COP8SAC744@TQFP44 [DX3002]
COP8SBE9@PLCC68 [DX2068]
COP8SBR9@PLCC68 [DX2068]
COP8SCE9@PLCC44 [DX2044]
COP8SCR9@PLCC44 [DX2044]
COP8SCR9@TQFP44 [DX3002]
COP87L88@TQFP44 [DX3002]
COP87L88EB@PLCC68 [DX2068]
COP880(CMHD) [DX0001]
COP881(CMHD) [DX0001]
COP884(CFMHD) [DX0001]
COP884(CGMHD) [DX0001]
COP884(CLMHD) [DX0001]
COP884(CSMHD) [DX0001]
COP884(EGMHD) [DX0001]
COP888(CFMHD) [DX0001]
COP888(CGMHD) [DX0001]
COP888(CLMHD) [DX0001]
COP888(CSMHD) [DX0001]
COP888(EGMHD) [DX0001]
COP8ACC720 [DX0001]
COP8ACC728 [DX0001]
COP8ALE728 [DX0001]
COP8AXE9 [DX0001]
COP8CBE9@PLCC44 [DX2044]
COP8CBR9@PLCC44 [DX2044]
COP8CBR9@TQFP44 [DX3002]
COP8CCE9@TQFP44 [DX3002]
COP8CCR9@PLCC68 [DX2068]
COP8CDR9@PLCC44 [DX2044]
COP8CDR9@TQFP44 [DX3002]
COP8CXG9@PLCC44 [DX2044]
COP8SAA716@SOIC16 [DX1033]
COP8SAA720@SOIC20 [DX1033]
COP8SAA728@PLCC28 [DX2028]
COP8SAA740 [DX0001]
COP8SAA744@PLCC44 [DX2044]
COP8SAB716 [DX0001]
COP8SAB720 [DX0001]
COP8SAB728 [DX0001]
COP8SAB728@SOIC28 [DX1033]
COP8SAB740@SOIC40 [DX1014]
COP8SAB744@TQFP44 [DX3002]
COP8SAC716@SOIC16 [DX1033]
COP8SAC720@SOIC20 [DX1033]
COP8SAC728@PLCC28 [DX2028]
COP8SAC740 [DX0001]
COP8SAC744@PLCC44 [DX2044]
COP8SBE9@PLCC44 [DX2044]
COP8SBR9@PLCC44 [DX2044]
COP8SBR9@TQFP44 [DX3002]
COP8SCE9@PLCC68 [DX2068]
COP8SCR9@PLCC68 [DX2068]
COP8SDR9@PLCC44 [DX2044]

COP8SDR9@PLCC68 [DX2068]
COP8SDR9@TQFP44 [DX3002]
COP8SGE720 [DX0001]
COP8SGE720@SOIC20 [DX1033]
COP8SGE728 [DX0001]
COP8SGE728@SOIC28 [DX1033]
COP8SGE740 [DX0001]
COP8SGE740@SOIC40 [DX1014]
COP8SGE744@PLCC44 [DX2044]
COP8SGE744@TQFP44 [DX3002]
COP8SGR720 [DX0001]
COP8SGR720@SOIC20 [DX1033]
COP8SGR728 [DX0001]
COP8SGR728@SOIC28 [DX1033]
COP8SGR740 [DX0001]
COP8SGR740@SOIC40 [DX1014]
COP8SGR744@PLCC44 [DX2044]
COP8SGR744@TQFP44 [DX3002]
COP943(CMHD) [DX0001]

NTE

E(E)PROM/FRAM/NVRAM

NTE2532 [DX0001]
NTE2532A [DX0001]
NTE25L32 [DX0001]

NUMONYX

E(E)PROM/FRAM/NVRAM

JR28F032M29EWB@TSOP48 [DX1004]
JR28F032M29EWH@TSOP48 [DX1004]
JR28F032M29EWL@TSOP48 [DX1004]
JR28F032M29EWT@TSOP48 [DX1004]
JR28F064M29EWB@TSOP48 [DX1004]
JR28F064M29EWH@TSOP48 [DX1004]
JR28F064M29EWL@TSOP48 [DX1004]
JR28F064M29EWT@TSOP48 [DX1004]
JS28F00AM29EWH@TSOP56 [DX1055]
JS28F00AM29EWHS@TSOP56 [DX1055]
JS28F00AM29EWL@TSOP56 [DX1055]
JS28F00AM29EWLS@TSOP56 [DX1055]
JS28F00AP30BF@TSOP56 [DX1011]
JS28F00AP30EF@TSOP56 [DX1011]
JS28F00AP30TF@TSOP56 [DX1011]
JS28F00AP33BF@TSOP56 [DX1011]
JS28F00AP33EF@TSOP56 [DX1011]
JS28F00AP33TF@TSOP56 [DX1011]
JS28F00BM29EWH@TSOP56 [DX1055]
JS28F064M29EWB@TSOP56 [DX1055]
JS28F064M29EWH@TSOP56 [DX1055]
JS28F064M29EWL@TSOP56 [DX1055]
JS28F064M29EWT@TSOP56 [DX1055]
JS28F128J3F@TSOP56 [DX1011]
JS28F128M29EWH@TSOP56 [DX1055]
JS28F128M29EWL@TSOP56 [DX1055]
JS28F128M29EWLD@TSOP56 [DX1055]
JS28F128P30BF@TSOP56 [DX1011]
JS28F128P30TF@TSOP56 [DX1011]
JS28F128P33BF@TSOP56 [DX1011]
JS28F128P33TF@TSOP56 [DX1011]
JS28F256J3F@TSOP56 [DX1011]
JS28F256M29EWH@TSOP56 [DX1055]
JS28F256M29EWHS@TSOP56 [DX1055]
JS28F256M29EWL@TSOP56 [DX1055]
JS28F256M29EWLS@TSOP56 [DX1055]
JS28F256P30BF@TSOP56 [DX1011]
JS28F256P30TF@TSOP56 [DX1011]
JS28F256P33BF@TSOP56 [DX1011]
JS28F256P33TF@TSOP56 [DX1011]
JS28F320J3F@TSOP56 [DX1011]
JS28F512M29AWH@FBGA56 [DX1055]
JS28F512M29AWL@FBGA56 [DX1055]
JS28F512M29EWH@TSOP56 [DX1055]
JS28F512M29EWHS@TSOP56 [DX1055]
JS28F512M29EWL@TSOP56 [DX1055]
JS28F512M29EWLS@TSOP56 [DX1055]
JS28F512P30BF@TSOP56 [DX1011]

JS28F512P30EF@TSOP56 [DX1011]
JS28F512P30TF@TSOP56 [DX1011]
JS28F512P33BF@TSOP56 [DX1011]
JS28F512P33EF@TSOP56 [DX1011]
JS28F512P33TF@TSOP56 [DX1011]
JS28F640J3F@TSOP56 [DX1011]
JS28F640P30BF@TSOP56 [DX1011]
JS28F640P30TF@TSOP56 [DX1011]
JS28F640P33BF@TSOP56 [DX1011]
JS28F640P33TF@TSOP56 [DX1011]
JZ58F0049M0Y0GE@FBGA128 [DX5087]
JZ58F0049M0Y0GF@FBGA128 [DX5087]
JZ58F0049M0Y0GG@FBGA128 [DX5087]
JZ58F0049M0Y0GH@FBGA128 [DX5087]
JZ58F0070M0Y0KE@FBGA160 [DX5105]
JZ58F0084M0Y1GE@BGA128 [DX5087]
JZ58F0084M0Y1GF@BGA128 [DX5087]
JZ58F0084M0Y1GG@BGA128 [DX5087]
M25P05-A@SO8 [DX1045#1]
M25P05-A@TSSOP8 [DX1059#3]
M25P05-A@UFDFPN8 [DX4002#1]
M25P05-A@VFQFPN8 [DX4005#1]
M25P10-A@SOIC8 [DX1045#1]
M25P10-A@UFDFPN8 [DX4002#1]
M25P10-A@VFQFPN8 [DX4005#1]
M25P128@SO16 [DX1072#1]
M25P128@VDFPN8 [DX4006#1]
M25P20@QFN8L [DX4005#1]
M25P20@SO8 [DX1045#1]
M25P20@VFQFPN8 [DX4005#1]
M25P40@DFN8 [DX4005#1]
M25P40@SO8N [DX1045#1]
M25P40@SO8W [DX1044#1]
M25P40@VFDFPN8 [DX4005#1]
M25P40MB@UFDFPN8 [DX4002#1]
M25P40MC@UFDFPN8 [DX4076]
M25P64@SO16 [DX1072#1]
M25P64@VDFPN8 [DX4006#1]
M25P80 [DX0001]
M25P80@SOIC8(150 mil) [DX1045#1]
M25P80@SOIC8(200 mil) [DX1044#1]
M25P80@UFDFPN8 [DX4002#1]
M25P80@VFDFPN8 [DX4005#1]
M25PE10@SO8N [DX1045#1]
M25PE10@VFQFPN8 [DX4005#1]
M25PE16@SO8W [DX1044#1]
M25PE16@VFQFPN8 [DX4005#1]
M25PE20@SO8N [DX1045#1]
M25PE20@VFQFPN8 [DX4005#1]
M25PE40@SO8N [DX1045#1]
M25PE40@SO8W [DX1044#1]
M25PE40@VFQFPN8 [DX4005#1]
M25PE80@QFN8L [DX4005#1]
M25PE80@SO8N [DX1045#1]
M25PE80@SO8W [DX1044#1]
M25PE80@VFQFPN8 [DX4005#1]
M25PX16@SOIC16 [DX1033#1]
M25PX16@SOIC8(150 mil) [DX1045#1]
M25PX16@SOIC8(200 mil) [DX1044#1]
M25PX16@TBGA24 [DX5157]
M25PX16@VFQFPN8 [DX4005#1]
M25PX32@SOIC16 [DX1033#1]
M25PX32@SOIC8 [DX1044#1]
M25PX32@TBGA24 [DX5157]
M25PX32@VFQFPN8 [DX4005#1]
M25PX64@SOIC16 [DX1033#1]
M25PX64@TBGA24 [DX5157]
M25PX64@VDFPN8 [DX4006#1]
M25PX80 [DX0001#1]
M25PX80@SOIC8[150mil] [DX1045#1]
M25PX80@SOIC8[200mil] [DX1044#1]
M25PX80@VFQFPN8 [DX4005#1]
M28W320ECB@FBGA48 [DX5031]
M28W320ECB@TSOP48 [DX1004]
M28W320ECT@FBGA48 [DX5031]
M28W320ECT@TSOP48 [DX1004]
M28W320FCB@FBGA48 [DX5031]
M28W320FCB@TSOP48 [DX1004]
M28W320FCT@FBGA48 [DX5031]
M28W320FCT@TSOP48 [DX1004]
M28W640ECB@FBGA48 [DX5078]
M28W640ECB@TSOP48 [DX1004]
M28W640ECT@FBGA48 [DX5078]
M28W640ECT@TSOP48 [DX1004]
M28W640FCB@FBGA48 [DX5078]
M28W640FCB@TSOP48 [DX1004]
M28W640FCT@FBGA48 [DX5078]
M28W640FCT@TSOP48 [DX1004]
M28W640HCB@FBGA48 [DX5078]
M28W640HCB@TSOP48 [DX1004]
M28W640HCT@FBGA48 [DX5078]
M28W640HCT@TSOP48 [DX1004]
M29DW127G@FBGA64 [DX5004]

M29DW127G@TSOP56 [DX1011]
M29DW128G@FBGA64 [DX5004]
M29DW128G@TSOP56 [DX1055]
M29DW256G@LFBGA64 [DX5074]
M29DW256G@TFBGA64 [DX5004]
M29DW256G@TSOP56 [DX1055]
M29F160FB@FBGA48 [DX5002]
M29F160FB@TSOP48 [DX1043]
M29F160FT@FBGA48 [DX5002]
M29F160FT@TSOP48 [DX1043]
M29F200FB@FBGA48 [DX5002]
M29F200FB@PSOP44 [DX1014]
M29F200FB@TSOP48 [DX1043]
M29F200FT@FBGA48 [DX5002]
M29F200FT@PSOP44 [DX1014]
M29F200FT@TSOP48 [DX1043]
M29F400FB@FBGA48 [DX5002]
M29F400FB@PSOP44 [DX1014]
M29F400FB@TSOP48 [DX1043]
M29F400FT@FBGA48 [DX5002]
M29F400FT@PSOP44 [DX1014]
M29F400FT@TSOP48 [DX1043]
M29F800FB@FBGA48 [DX5002]
M29F800FB@PSOP44 [DX1014]
M29F800FB@TSOP48 [DX1043]
M29F800FT@FBGA48 [DX5002]
M29F800FT@PSOP44 [DX1014]
M29F800FT@TSOP48 [DX1043]
M29W064FB@FBGA48 [DX5002]
M29W064FB@TSOP48 [DX1004]
M29W064FT@FBGA48 [DX5002]
M29W064FT@TSOP48 [DX1004]
M29W128GSH@FBGA64 [DX5004]
M29W128GSH@FBGA64(ZS) [DX5074]
M29W128GSH@TSOP56 [DX1055]
M29W128GSL@FBGA64 [DX5004]
M29W128GSL@FBGA64(ZS) [DX5074]
M29W128GSL@TSOP56 [DX1055]
M29W160DB@LBGA48 [DX5022]
M29W160DB@PSOP44 [DX1014]
M29W160DB@TSOP48 [DX1004]
M29W160DT@LBGA48 [DX5022]
M29W160DT@PSOP44 [DX1014]
M29W160DT@TSOP48 [DX1004]
M29W160EB@LBGA48 [DX5002]
M29W160EB@LBGA64 [DX5074]
M29W160EB@PSOP44 [DX1014]
M29W160EB@TSOP48 [DX1004]
M29W160ET@LBGA48 [DX5002]
M29W160ET@LBGA64 [DX5074]
M29W160ET@PSOP44 [DX1014]
M29W160ET@TSOP48 [DX1004]
M29W160FB@LBGA48 [DX5002]
M29W160FB@TSOP48 [DX1004]
M29W160FT@LBGA48 [DX5002]
M29W160FT@TSOP48 [DX1004]
M29W256GH@LFBGA64 [DX5074]
M29W256GH@TFBGA64 [DX5004]
M29W256GH@TSOP56 [DX1055]
M29W256GL@LFBGA64 [DX5074]
M29W256GL@TFBGA64 [DX5004]
M29W256GL@TSOP56 [DX1055]
M29W320EB@FBGA48 [DX5002]
M29W320EB@FBGA64 [DX5074]
M29W320EB@TSOP48 [DX1004]
M29W320ET@FBGA48 [DX5002]
M29W320ET@FBGA64 [DX5074]
M29W320ET@TSOP48 [DX1004]
M29W400DB(ZA)@LBGA48 [DX5039]
M29W400DB(ZE)@LBGA48 [DX5002]
M29W400DB@PSOP44 [DX1014]
M29W400DB@TSOP48 [DX1004]
M29W400DT(ZA)@LBGA48 [DX5039]
M29W400DT(ZE)@LBGA48 [DX5002]
M29W400DT@PSOP44 [DX1014]
M29W400DT@TSOP48 [DX1004]
M29W400FB@FBGA48 [DX5002]
M29W400FB@TSOP48 [DX1004]
M29W400FT@FBGA48 [DX5002]
M29W400FT@TSOP48 [DX1004]
M29W512GH@TSOP56 [DX1055]
M29W640DB@FBGA63 [DX5047]
M29W640DB@TSOP48 [DX1004]
M29W640DT@FBGA63 [DX5047]
M29W640DT@TSOP48 [DX1004]
M29W641DH@TSOP48 [DX1004]
M29W641DL@TSOP48 [DX1004]
M29W641DU@FBGA63 [DX5047]
M29W800DB@FBGA48 [DX5002]
M29W800DB@PSOP44 [DX1014]
M29W800DB@TSOP48 [DX1004]
M29W800DT@FBGA48 [DX5002]
M29W800DT@PSOP44 [DX1014]
M29W800DT@TSOP48 [DX1004]
M29W800FB@FBGA48 [DX5039]
M29W800FB@TSOP48 [DX1004]

M29W800FT@FBGA48 [DX5039]
M30L0R7000B0@FBGA88 [DX5005]
M30L0R8000B0@FBGA88 [DX5005]
M30L0R8000T0@FBGA88 [DX5005]
M36C0W5030B0@FBGA56 [DX5045]
M36C0W5040B0@FBGA56 [DX5045]
M36C0W6040B0@FBGA56 [DX5045]
M36C0W6050B0@FBGA56 [DX5045]
M36L0R7040B0@FBGA88 [DX5005]
M36L0R7050B0@FBGA88 [DX5005]
M36L0R7050B2@FBGA88 [DX5005]
M36L0R7050B4@FBGA80 [DX5052]
M36L0R7050L3@FBGA56 [DX5099]
M36L0R7050T0@FBGA88 [DX5005]
M36L0R7050T2@FBGA88 [DX5005]
M36L0R7050T4@FBGA80 [DX5052]
M36L0R7050U3@FBGA56 [DX5099]
M36L0R7060B1@FBGA88 [DX5005]
M36L0R7060L3@FBGA56 [DX5099]
M36L0R7060T1@FBGA88 [DX5005]
M36L0R7060U3@FBGA56 [DX5099]
M36L0R7070U3@FBGA133 [DX5069]
M36L0R8050L3@FBGA88 [DX5005]
M36L0R8050U3@FBGA88 [DX5005]
M36L0R8060B1@FBGA88 [DX5005]
M36L0R8060B5@FBGA88 [DX5005]
M36L0R8060B9@FBGA88 [DX5005]
M36L0R8060L3@FBGA80 [DX5052]
M36L0R8060T0@FBGA88 [DX5005]
M36L0R8060T3@FBGA88 [DX5005]
M36L0R8060T8@FBGA88 [DX5005]
M36L0R8060U3@FBGA56 [DX5099]
M36L0R8060U3@FBGA88 [DX5005]
M36L0T7040T0@FBGA88 [DX5005]
M36L0T7050B1@FBGA88 [DX5005]
M36L0T7050B3@FBGA80 [DX5052]
M36L0T7050T0@FBGA88 [DX5005]
M36L0T7050T2@FBGA88 [DX5005]
M36L0T7050T3@FBGA88 [DX5005]
M36L0T7060B1@FBGA88 [DX5005]
M36L0T7060B3@FBGA88 [DX5005]
M36L0T7060T1@FBGA88 [DX5005]
M36L0T7060T3@FBGA88 [DX5005]
M36L0T8050B1@FBGA88 [DX5005]
M36L0T8050T0@FBGA88 [DX5005]
M36L0T8050T3@FBGA88 [DX5005]
M36L0T8060B1@FBGA88 [DX5005]
M36L0T8060B3@FBGA88 [DX5005]
M29W800FT@TSOP48 [DX1004]
M30L0R7000T0@FBGA88 [DX5005]
M30L0R8000B2@FBGA88 [DX5005]
M30L0R8000T2@FBGA88 [DX5005]
M36C0W5030T0@FBGA56 [DX5045]
M36C0W5040T0@FBGA56 [DX5045]
M36C0W6040T0@FBGA56 [DX5045]
M36C0W6050T0@FBGA56 [DX5045]
M36L0R7040T0@FBGA88 [DX5005]
M36L0R7050B1@FBGA88 [DX5005]
M36L0R7050B3@FBGA80 [DX5052]
M36L0R7050B4@FBGA88 [DX5005]
M36L0R7050L3@FBGA88 [DX5005]
M36L0R7050T1@FBGA88 [DX5005]
M36L0R7050T3@FBGA80 [DX5052]
M36L0R7050T4@FBGA88 [DX5005]
M36L0R7050U3@FBGA88 [DX5005]
M36L0R7060B2@FBGA88 [DX5005]
M36L0R7060L3@FBGA88 [DX5005]
M36L0R7060T2@FBGA88 [DX5005]
M36L0R7060U3@FBGA88 [DX5005]
M36L0R8050L3@FBGA56 [DX5099]
M36L0R8050U3@FBGA56 [DX5099]
M36L0R8060B0@FBGA88 [DX5005]
M36L0R8060B3@FBGA88 [DX5005]
M36L0R8060B8@FBGA88 [DX5005]
M36L0R8060L3@FBGA56 [DX5099]
M36L0R8060L3@FBGA88 [DX5005]
M36L0R8060T1@FBGA88 [DX5005]
M36L0R8060T5@FBGA88 [DX5005]
M36L0R8060T9@FBGA88 [DX5005]
M36L0R8060U3@FBGA80 [DX5052]
M36L0T7040B0@FBGA88 [DX5005]
M36L0T7050B0@FBGA88 [DX5005]
M36L0T7050B2@FBGA88 [DX5005]
M36L0T7050B3@FBGA88 [DX5005]
M36L0T7050T1@FBGA88 [DX5005]
M36L0T7050T3@FBGA80 [DX5052]
M36L0T7060B0@FBGA88 [DX5005]
M36L0T7060B2@FBGA88 [DX5005]
M36L0T7060T0@FBGA88 [DX5005]
M36L0T7060T2@FBGA88 [DX5005]
M36L0T8050B0@FBGA88 [DX5005]
M36L0T8050B3@FBGA88 [DX5005]
M36L0T8050T1@FBGA88 [DX5005]
M36L0T8060B0@FBGA88 [DX5005]
M36L0T8060B3@FBGA80 [DX5052]
M36L0T8060T0@FBGA88 [DX5005]

M36L0T8060T1@FBGA88 [DX5005]
M36L0T8060T3@FBGA80 [DX5052]
M36L0T8060T3@FBGA88 [DX5005]
M36P0R8060E0ZAC@FBGA107 [DX5077]
M36P0R8060N0ZS@FBGA56 [DX5099]
M36P0R8070N0ZS@FBGA56 [DX5099]
M36P0R9060E0ZAC@FBGA107 [DX5077]
M36P0R9070E0ZAC@FBGA107 [DX5077]
M36P0R9070E1ZAC@FBGA107 [DX5077]
M36W0R5020B0(EFP)@FBGA88 [DX5005]
M36W0R5020B0(Q_Word)@FBGA88 [DX5005]
M36W0R5020T0(EFP)@FBGA88 [DX5005]
M36W0R5020T0(Q_Word)@FBGA88 [DX5005]
M36W0R5030B0(EFP)@FBGA88 [DX5005]
M36W0R5030B0(Q_Word)@FBGA88 [DX5005]
M36W0R5030T0(EFP)@FBGA88 [DX5005]
M36W0R5030T0(Q_Word)@FBGA88 [DX5005]
M36W0R5030U5@TFBGA52 [DX5127]
M36W0R5030U5@TFBGA88 [DX5005]
M36W0R5040B0(EFP)@FBGA88 [DX5005]
M36W0R5040B0(Q_Word)@FBGA88 [DX5005]
M36W0R5040B1(EFP)@FBGA88 [DX5005]
M36W0R5040B1(Q_Word)@FBGA88 [DX5005]
M36W0R5040B2(EFP)@FBGA88 [DX5005]
M36W0R5040B2(Q_Word)@FBGA88 [DX5005]
M36W0R5040B4(EFP)@FBGA88 [DX5005]
M36W0R5040B4(Q_Word)@FBGA88 [DX5005]
M36W0R5040B5(EFP)@FBGA88 [DX5005]
M36W0R5040B5(Q_Word)@FBGA88 [DX5005]
M36W0R5040B7(EFP)@FBGA88 [DX5005]
M36W0R5040B7(Q_Word)@FBGA88 [DX5005]
M36W0R5040L3@FBGA88 [DX5005]
M36W0R5040L3@TFBGA56 [DX5127]
M36W0R5040L4@TFBGA56 [DX5099]
M36W0R5040L4@TFBGA88 [DX5005]
M36W0R5040L6@TFBGA52 [DX5127]
M36W0R5040L6@TFBGA88 [DX5005]
M36W0R5040T0(EFP)@FBGA88 [DX5005]
M36W0R5040T0(Q_Word)@FBGA88 [DX5005]
M36W0R5040T1(EFP)@FBGA88 [DX5005]
M36W0R5040T1(Q_Word)@FBGA88 [DX5005]
M36W0R5040T2(EFP)@FBGA88 [DX5005]
M36W0R5040T2(Q_Word)@FBGA88 [DX5005]
M36W0R5040T4(EFP)@FBGA88 [DX5005]
M36W0R5040T4(Q_Word)@FBGA88 [DX5005]
M36W0R5040T5(EFP)@FBGA88 [DX5005]
M36W0R5040T5(Q_Word)@FBGA88 [DX5005]
M36W0R5040T7(EFP)@FBGA88 [DX5005]
M36W0R5040T7(Q_Word)@FBGA88 [DX5005]
M36W0R5040U3@FBGA88 [DX5005]
M36W0R5040U3@TFBGA56 [DX5127]
M36W0R5040U4@TFBGA56 [DX5099]
M36W0R5040U4@TFBGA88 [DX5005]
M36W0R5040U5@TFBGA52 [DX5127]
M36W0R5040U5@TFBGA88 [DX5005]
M36W0R5040U6@TFBGA52 [DX5127]
M36W0R5040U6@TFBGA88 [DX5005]
M36W0R5050L6@TFBGA52 [DX5127]
M36W0R5050L6@TFBGA88 [DX5005]
M36W0R5050U6@TFBGA52 [DX5127]
M36W0R5050U6@TFBGA88 [DX5005]
M36W0R6030B0(EFP)@FBGA88 [DX5005]

M36W0R6030B0(Q_Word)@FBGA88 [DX5005]
M36W0R6030T0(EFP)@FBGA88 [DX5005]
M36W0R6030T0(Q_Word)@FBGA88 [DX5005]
M36W0R6040B0(EFP)@FBGA88 [DX5005]
M36W0R6040B0(Q_Word)@FBGA88 [DX5005]
M36W0R6040B1(EFP)@FBGA88 [DX5005]
M36W0R6040B1(Q_Word)@FBGA88 [DX5005]
M36W0R6040B3(EFP)@FBGA88 [DX5005]
M36W0R6040B3(Q_Word)@FBGA88 [DX5005]
M36W0R6040B4(EFP)@FBGA88 [DX5005]
M36W0R6040B4(Q_Word)@FBGA88 [DX5005]
M36W0R6040B7(EFP)@FBGA88 [DX5005]
M36W0R6040B7(Q_Word)@FBGA88 [DX5005]
M36W0R6040L3@FBGA88 [DX5005]　　M36W0R6040L4@TFBGA56 [DX5099]
M36W0R6040L4@TFBGA88 [DX5005]　　M36W0R6040L6@TFBGA52 [DX5127]
M36W0R6040L6@TFBGA88 [DX5005]
M36W0R6040T0(EFP)@FBGA88 [DX5005]
M36W0R6040T0(Q_Word)@FBGA88 [DX5005]
M36W0R6040T1(EFP)@FBGA88 [DX5005]
M36W0R6040T1(Q_Word)@FBGA88 [DX5005]
M36W0R6040T3(EFP)@FBGA88 [DX5005]
M36W0R6040T3(Q_Word)@FBGA88 [DX5005]
M36W0R6040T4(EFP)@FBGA88 [DX5005]
M36W0R6040T4(Q_Word)@FBGA88 [DX5005]
M36W0R6040T7(EFP)@FBGA88 [DX5005]
M36W0R6040T7(Q_Word)@FBGA88 [DX5005]
M36W0R6040U3@FBGA88 [DX5005]　　M36W0R6040U4@TFBGA56 [DX5099]
M36W0R6040U4@TFBGA88 [DX5005]　　M36W0R6040U5@TFBGA52 [DX5127]
M36W0R6040U5@TFBGA88 [DX5005]　　M36W0R6040U6@TFBGA52 [DX5127]
M36W0R6040U6@TFBGA88 [DX5005]
M36W0R6050B0(EFP)@FBGA88 [DX5005]
M36W0R6050B0(Q_Word)@FBGA88 [DX5005]
M36W0R6050B1(EFP)@FBGA88 [DX5005]
M36W0R6050B1(Q_Word)@FBGA88 [DX5005]
M36W0R6050B3(EFP)@FBGA88 [DX5005]
M36W0R6050B3(Q_Word)@FBGA88 [DX5005]
M36W0R6050B4(EFP)@FBGA88 [DX5005]
M36W0R6050B4(Q_Word)@FBGA88 [DX5005]
M36W0R6050L0@FBGA88 [DX5005]　　M36W0R6050L4@TFBGA56 [DX5099]
M36W0R6050L4@TFBGA88 [DX5005]　　M36W0R6050L6@TFBGA52 [DX5127]
M36W0R6050L6@TFBGA88 [DX5005]
M36W0R6050T0(EFP)@FBGA88 [DX5005]
M36W0R6050T0(Q_Word)@FBGA88 [DX5005]
M36W0R6050T1(EFP)@FBGA88 [DX5005]
M36W0R6050T1(Q_Word)@FBGA88 [DX5005]
M36W0R6050T3(EFP)@FBGA88 [DX5005]
M36W0R6050T3(Q_Word)@FBGA88 [DX5005]
M36W0R6050T4(EFP)@FBGA88 [DX5005]

M36W0R6050T4(Q_Word)@FBGA88 [DX5005]
M36W0R6050U0@FBGA88 [DX5005]
M36W0R6050U4@TFBGA88 [DX5005]
M36W0R6050U5@TFBGA88 [DX5005]
M36W0R6050U6@TFBGA88 [DX5005]
M36W0R6050U4@TFBGA56 [DX5099]
M36W0R6050U5@TFBGA56 [DX5099]
M36W0R6050U6@TFBGA52 [DX5127]
M36W0R7050B0(EFP)@FBGA88 [DX5005]
M36W0R7050B0(Q_Word)@FBGA88 [DX5005]
M36W0R7050T0(EFP)@FBGA88 [DX5005]
M36W0R7050T0(Q_Word)@FBGA88 [DX5005]
M36W0T5040B1(EFP)@FBGA88 [DX5005]
M36W0T5040B1(Q_Word)@FBGA88 [DX5005]
M36W0T5040T1(EFP)@FBGA88 [DX5005]
M36W0T5040T1(Q_Word)@FBGA88 [DX5005]
M36W0T6030B0(EFP)@FBGA88 [DX5005]
M36W0T6030B0(Q_Word)@FBGA88 [DX5005]
M36W0T6030T0(EFP)@FBGA88 [DX5005]
M36W0T6030T0(Q_Word)@FBGA88 [DX5005]
M36W0T6040B0(EFP)@FBGA88 [DX5005]
M36W0T6040B0(Q_Word)@FBGA88 [DX5005]
M36W0T6040B1(EFP)@FBGA88 [DX5005]
M36W0T6040B1(Q_Word)@FBGA88 [DX5005]
M36W0T6040B3(EFP)@FBGA88 [DX5005]
M36W0T6040B3(Q_Word)@FBGA88 [DX5005]
M36W0T6040T0(EFP)@FBGA88 [DX5005]
M36W0T6040T0(Q_Word)@FBGA88 [DX5005]
M36W0T6040T1(EFP)@FBGA88 [DX5005]
M36W0T6040T1(Q_Word)@FBGA88 [DX5005]
M36W0T6040T3(EFP)@FBGA88 [DX5005]
M36W0T6040T3(Q_Word)@FBGA88 [DX5005]
M36W0T6050B0(EFP)@FBGA88 [DX5005]
M36W0T6050B0(Q_Word)@FBGA88 [DX5005]
M36W0T6050B3(EFP)@FBGA88 [DX5005]
M36W0T6050B3(Q_Word)@FBGA88 [DX5005]
M36W0T6050T0(EFP)@FBGA88 [DX5005]
M36W0T6050T0(Q_Word)@FBGA88 [DX5005]
M36W0T6050T3(EFP)@FBGA88 [DX5005]
M36W0T6050T3(Q_Word)@FBGA88 [DX5005]
M36W0T7040B0(EFP)@FBGA88 [DX5005]
M36W0T7040B0(Q_Word)@FBGA88 [DX5005]
M36W0T7040T0(EFP)@FBGA88 [DX5005]
M36W0T7040T0(Q_Word)@FBGA88 [DX5005]
M36W0T7050B0(EFP)@FBGA88 [DX5005]
M36W0T7050B0(Q_Word)@FBGA88 [DX5005]
M36W0T7050T0(EFP)@FBGA88 [DX5005]
M36W0T7050T0(Q_Word)@FBGA88 [DX5005]
M39L0R8090U3@FBGA133 [DX5069]
M45PE10@VFQPN8 [DX4005#1]
M45PE16@VFQFPN8 [DX4005#1]
M45PE10@SO8N [DX1045#1]
M45PE16@SO8W [DX1044#1]
M45PE20@SO8 [DX1045#1]

M45PE20@VFQFPN8 [DX4005#1]
M45PE40@SO8W [DX1044#1]
M45PE80@QFN8L [DX4005#1]
M45PE80@SO8W [DX1044#1]
M58LR128KB@FBGA56 [DX5032]
M58LR128KT@FBGA56 [DX5032]
M58LR256KB@FBGA79 [DX5164]
M58LR256KT@FBGA79 [DX5164]
M58LT128KSB@FBGA64 [DX5004]
M58LT256JSB@FBGA64 [DX5004]
M58LT256KSB@FBGA64 [DX5004]
M58PR001LE@TFGBA105 [DX5056]
M58PR512LE@TFGBA105 [DX5056]
M58WR016KB(EFP)@FBGA56 [DX5032]
M58WR016KB(Q_Word)@FBGA56 [DX5032]
M58WR016KB(Q_Word)@FBGA88 [DX5005]
M58WR016KT(EFP)@FBGA56 [DX5032]
M58WR016KT(Q_Word)@FBGA56 [DX5032]
M58WR016KT(Q_Word)@FBGA88 [DX5005]
M58WR032KB(EFP)@FBGA56 [DX5032]
M58WR032KB(Q_Word)@FBGA56 [DX5032]
M58WR032KB(Q_Word)@FBGA88 [DX5005]
M58WR032KT(EFP)@FBGA56 [DX5032]
M58WR032KT(Q_Word)@FBGA56 [DX5032]
M58WR032KT(Q_Word)@FBGA88 [DX5005]
M58WR064KB(EFP)@FBGA56 [DX5032]
M58WR064KB(Q_Word)@FBGA56 [DX5032]
M58WR064KB(Q_Word)@FBGA88 [DX5005]
M58WR064KT(EFP)@FBGA56 [DX5032]
M58WR064KT(Q_Word)@FBGA56 [DX5032]
M58WR064KT(Q_Word)@FBGA88 [DX5005]
M58WT032KB(EFP)@FBGA88 [DX5005]
M58WT032KB(Q_Word)@FBGA88 [DX5005]
M58WT032KT(EFP)@FBGA88 [DX5005]
M58WT032KT(Q_Word)@FBGA88 [DX5005]
M58WT064KB(EFP)@FBGA88 [DX5005]
M58WT064KB(Q_Word)@FBGA88 [DX5005]
M58WT064KT(EFP)@FBGA88 [DX5005]
M58WT064KT(Q_Word)@FBGA88 [DX5005]
N25Q032@BGA24 [DX5157]
N25Q032@BGA24(fast mode) [DX5157]
N25Q032@SOIC16 [DX1033#1]
N25Q032@SOIC16(fast mode) [DX1033#1]
N25Q032@SOIC8(150mil) [DX1045#1]
N25Q032@SOIC8(150mil)(fast mode) [DX1045#1]
N25Q032@SOIC8(208mil) [DX1044#1]
N25Q032@SOIC8(208mil)(fast mode) [DX1044#1]
N25Q032@VDFPN8(6*5mm) [DX4005#1]
M45PE40@SO8N [DX1045#1]
M45PE40@VFQFPN8 [DX4005#1]
M45PE80@SO8N [DX1045#1]
M45PE80@VFQFPN8 [DX4005#1]
M58LR128KB@FBGA88 [DX5005]
M58LR128KT@FBGA88 [DX5005]
M58LR256KB@FBGA88 [DX5005]
M58LR256KT@FBGA88 [DX5005]
M58LT128KST@FBGA64 [DX5004]
M58LT256JST@FBGA64 [DX5004]
M58LT256KST@FBGA64 [DX5004]
M58PR001LE@TFGBA107 [DX5077]
M58PR512LE@TFGBA107 [DX5077]
M58WR016KB(EFP)@FBGA88 [DX5005]
M58WR016KT(EFP)@FBGA88 [DX5005]
M58WR032KB(EFP)@FBGA88 [DX5005]
M58WR032KT(EFP)@FBGA88 [DX5005]
M58WR064KB(EFP)@FBGA88 [DX5005]
M58WR064KT(EFP)@FBGA88 [DX5005]

N25Q032@VDFPN8(6*5mm)(fast mode) [DX4005#1]
N25Q032@VDFPN8(8*6mm) [DX4006#1]
N25Q032@VDFPN8(8*6mm)(fast mode) [DX4006#1]
N25Q064@BGA24 [DX5157]
N25Q064@BGA24(fast mode) [DX5157]
N25Q064@SOIC16 [DX1033#1]
N25Q064@SOIC16(fast mode) [DX1033#1]
N25Q064@SOIC8(150mil) [DX1045#1]
N25Q064@SOIC8(150mil)(fast mode) [DX1045#1]
N25Q064@SOIC8(208mil) [DX1044#1]
N25Q064@SOIC8(208mil)(fast mode) [DX1044#1]
N25Q064@VDFPN8(6*5mm) [DX4005#1]
N25Q064@VDFPN8(6*5mm)(fast mode) [DX4005#1]
N25Q064@VDFPN8(8*6mm) [DX4006#1]
N25Q064@VDFPN8(8*6mm)(fast mode) [DX4006#1]
N25Q064A@BGA24 [DX5157]
N25Q064A@SOIC16 [DX1033#1]
N25Q064A@SOIC8(150mil) [DX1045#1]
N25Q064A@SOIC8(208mil) [DX1044#1]
N25Q064A@VDFPN8(6*5mm) [DX4005#1]
N25Q064A@VDFPN8(8*6mm) [DX4006#1]
N25Q128@BGA24 [DX5157]
N25Q128@BGA24(JIUZHOU) [DX5157]
N25Q128@SOIC16 [DX1072#1]
N25Q128@VDFPN8 [DX4006#1]
N25Q128A11B@BGA24 [DX5157]
N25Q128A11B@SOIC16 [DX1072#1]
N25Q128A11B@VDFPN8 [DX4006#1]
N25Q128A11E@BGA24 [DX5157]
N25Q128A11E@SOIC16 [DX1072#1]
N25Q128A11E@VDFPN8 [DX4006#1]
N25Q128A11T@BGA24 [DX5157]
N25Q128A11T@SOIC16 [DX1072#1]
N25Q128A11T@VDFPN8 [DX4006#1]
N25Q128A13B@BGA24 [DX5157]
N25Q128A13B@SOIC16 [DX1072#1]
N25Q128A13B@VDFPN8 [DX4006#1]
N25Q128A13E@BGA24 [DX5157]
N25Q128A13E@SOIC16 [DX1072#1]
N25Q128A13E@VDFPN8 [DX4006#1]
N25Q128A13T@BGA24 [DX5157]
N25Q128A13T@SOIC16 [DX1072#1]
N25Q128A13T@VDFPN8 [DX4006#1]
N25Q256A@BGA24 [DX5157]
N25Q256A@SOIC16 [DX1072#1]
N25Q256A@VDFPN8 [DX4006#1]
N25Q256A11E1240E [DX5157]
N25Q256A11E1240F [DX5157]
N25Q256A11EF840E [DX4006#1]
N25Q256A11EF840F [DX4006#1]
N25Q256A11ESF40F [DX1033#1]
N25Q256A11ESF40G [DX1033#1]
N25Q256A13E1240E [DX5157]
N25Q256A13E1240F [DX5157]
N25Q256A13EF840E [DX4006#1]
N25Q256A13EF840F [DX4006#1]
N25Q256A13ESF40F [DX1033#1]
N25Q256A13ESF40G [DX1033#1]
N25Q256A13Ex@BGA24 [DX5157]
N25Q256A13Ex@SOIC16 [DX1072#1]
N25Q256A13Ex@VDFPN8 [DX4006#1]
N3L0219071F5620@FBGA64 [DX5066]
N3L0219081F5620@FBGA64 [DX5066]
N3L0219091F5620@FBGA64 [DX5066]
N3L0619091F5310E@FBGA132 [DX5069]
N3L0619091F5310F@FBGA132 [DX5069]
NP8P128A13B@FBGA64 [DX5019]
NP8P128A13B@TSOP56 [DX1011]
NP8P128A13T@FBGA64 [DX5019]
NP8P128A13T@TSOP56 [DX1011]
PC28F00AG18F@FBGA64 [DX5019]
PC28F00AM29EWH@FBGA64 [DX5074]
PC28F00AM29EWHS@FBGA64 [DX5074]
PC28F00AM29EWL@FBGA64 [DX5074]

PC28F00AM29EWLS@FBGA64 [DX5074]
PC28F00AP30BF@FBGA64 [DX5019]
PC28F00AP30EF@FBGA64 [DX5019]
PC28F00AP30TF@FBGA64 [DX5019]
PC28F00AP33BF@FBGA64 [DX5019]
PC28F00AP33EF@FBGA64 [DX5019]
PC28F00AP33TF@FBGA64 [DX5019]
PC28F00BM29EWH@FBGA64 [DX5074]
PC28F00BP30EF@FBGA64 [DX5019]
PC28F00BP33EF@FBGA64 [DX5019]
PC28F064M29EWB@FBGA64 [DX5074]
PC28F064M29EWH@FBGA64 [DX5074]
PC28F064M29EWL@FBGA64 [DX5074]
PC28F064M29EWT@FBGA64 [DX5074]
PC28F128G18F@FBGA64 [DX5019]
PC28F128J3F@FBGA64 [DX5004]
PC28F128M29EWH@FBGA64 [DX5074]
PC28F128M29EWL@FBGA64 [DX5074]
PC28F128P30BF@FBGA64 [DX5004]
PC28F128P30TF@FBGA64 [DX5004]
PC28F128P33BF@FBGA64 [DX5019]
PC28F128P33TF@FBGA64 [DX5019]
PC28F256G18F@FBGA64 [DX5019]
PC28F256J3F@FBGA64 [DX5004]
PC28F256M29EWH@FBGA64 [DX5074]
PC28F256M29EWHS@FBGA64 [DX5074]
PC28F256M29EWL@FBGA64 [DX5074]
PC28F256M29EWLS@FBGA64 [DX5074]
PC28F256P30BF@FBGA64 [DX5004]
PC28F256P30TF@FBGA64 [DX5004]
PC28F256P33BF@FBGA64 [DX5004]
PC28F256P33TF@FBGA64 [DX5004]
PC28F320J3F@FBGA64 [DX5004]
PC28F512G18F@FBGA64 [DX5019]
PC28F512M29AWH@FBGA64 [DX5074]
PC28F512M29AWL@FBGA64 [DX5074]
PC28F512M29EWH@FBGA64 [DX5074]
PC28F512M29EWHS@FBGA64 [DX5074]
PC28F512M29EWL@FBGA64 [DX5074]
PC28F512M29EWLS@FBGA64 [DX5074]
PC28F512P30BF@FBGA64 [DX5019]
PC28F512P30EF@FBGA64 [DX5019]
PC28F512P30TF@FBGA64 [DX5019]
PC28F512P33BF@FBGA64 [DX5019]
PC28F512P33EF@FBGA64 [DX5019]
PC28F512P33TF@FBGA64 [DX5019]
PC28F640J3F@FBGA64 [DX5004]
PC28F640P30BF@FBGA64 [DX5004]
PC28F640P30TF@FBGA64 [DX5004]
PC28F640P33BF@FBGA64 [DX5019]
PC28F640P33TF@FBGA64 [DX5019]
PC48F4400P0TB0E@FBGA64 [DX5004]
PC48F4400P0VB0E@FBGA64 [DX5004]
PF38F3040M0Y0CE@FBGA107 [DX5077]
PF38F3040M0Y0QE@FBGA88 [DX5005]
PF38F3040M0Y1QE@FBGA88 [DX5005]
PF38F3040M0Y3DE@FBGA56 [DX5094]
PF38F3040M0Y3DF@FBGA56 [DX5094]
PF38F3040M0Y3DF@FBGA56(new) [DX5094]
PF38F3040M0Y3QE@FBGA88 [DX5005]
PF38F3050M0Y0CE@FBGA107 [DX5077]
PF38F3050M0Y0CF@FBGA107 [DX5077]
PF38F3050M0Y0QE@FBGA88 [DX5005]
PF38F3050M0Y0QF@FBGA88 [DX5005]
PF38F3050M0Y3DE@FBGA56 [DX5094]
PF38F3050M0Y3DF@FBGA56 [DX5094]
PF38F3050M0Y3DG@FBGA56 [DX5094]
PF38F3050M0Y3DH@FBGA56 [DX5094]
PF38F3050M0Y3QE@FBGA88 [DX5005]
PF38F3050M0Y3QF@FBGA88 [DX5005]
PF38F3060M0Y0CE@FBGA107 [DX5077]
PF38F3060M0Y1EE@FBGA132 [DX5069]
PF38F3060M0Y1EF@FBGA132 [DX5069]
PF38F3060M0Y1EG@FBGA132 [DX5069]
PF38F3060M0Y1EH@FBGA132 [DX5069]
PF38F3070M0Y1EE@FBGA132 [DX5069]
PF38F4050L0YAQE@FBGA88 [DX5005]
PF38F4050L0YWQE@FBGA88 [DX5005]
PF38F4050M0Y0C0@FBGA107 [DX5077]
PF38F4050M0Y0CG@FBGA107 [DX5077]
PF38F4050M0Y0Q0@FBGA88 [DX5005]
PF38F4050M0Y1Q0@FBGA88 [DX5005]
PF38F4050M0Y3CE@FBGA107 [DX5077]
PF38F4050M0Y3DE@FBGA56 [DX5114]
PF38F4050M0Y3DF@FBGA56 [DX5094]
PF38F4050M0YEQ0@FBGA88 [DX5005]
PF38F4050M0YEQF@FBGA88 [DX5005]
PF38F4060M0Y0BE@FBGA105 [DX5056]
PF38F4060M0Y0C0@FBGA107 [DX5077]
PF38F4060M0Y0CE@FBGA107 [DX5077]
PF38F4060M0Y3CE@FBGA107 [DX5077]
PF38F4060M0Y3DE@FBGA56 [DX5114]
PF38F4060M0Y3DF@FBGA56 [DX5114]
PF38F4060M0Y3DG@FBGA56 [DX5114]
PF38F4060M0Y3DH@FBGA56 [DX5114]

PF38F4460LLYBB0@FBGA103 [DX5056]
PF38F4462LLYDB0@FBGA103 [DX5056]
PF38F4470LLYBB0@FBGA103 [DX5056]
PF38F5050L0Y3AE@FBGA64 [DX5066]
PF38F5050M0Y0C0@FBGA107 [DX5077]
PF38F5050M0Y0CE@FBGA107 [DX5077]
PF38F5060L0Y3AE@FBGA64 [DX5066]
PF38F5060M0Y0B0@FBGA105 [DX5056]
PF38F5060M0Y0BE@FBGA105 [DX5056]
PF38F5060M0Y0C0@FBGA107 [DX5077]
PF38F5060M0Y0CE@FBGA107 [DX5077]
PF38F5060M0Y0CF@FBGA107 [DX5077]
PF38F5060M0Y0CH@FBGA107 [DX5077]
PF38F5060M0Y0CJ@FBGA107 [DX5077]
PF38F5060M0Y1EE@FBGA132 [DX5069]
PF38F5060M0Y3CE@FBGA107 [DX5077]
PF38F5060M0Y3DE@FBGA56 [DX5134]
PF38F5060M0Y3DF@FBGA56 [DX5114]
PF38F5060M0Y3DG@FBGA56 [DX5114]
PF38F5060M0Y3DH@FBGA56 [DX5114]
PF38F5060M0Y3DJ@FBGA56 [DX5114]
PF38F5060M0Y3DK@FBGA56 [DX5114]
PF38F5066M0Y3DE@FBGA56 [DX5114]
PF38F5070L0Y3AE@FBGA64 [DX5066]
PF38F5070M0Y0B0@FBGA105 [DX5056]
PF38F5070M0Y0BE@FBGA105 [DX5056]
PF38F5070M0Y0CE@FBGA107 [DX5056]
PF38F5070M0Y0V0@FBGA165 [DX5111]
PF38F5070M0Y0VE@FBGA165 [DX5111]
PF38F5070M0Y1EE@FBGA132 [DX5069]
PF38F5070M0Y1V0@FBGA165 [DX5111]
PF38F5070M0Y1VE@FBGA165 [DX5111]
PF38F5070M0Y3CE@FBGA107 [DX5056]
PF38F5070M0Y3CF@FBGA107 [DX5056]
PF38F5070M0Y3DE@FBGA56 [DX5134]
PF38F5080M0Y0B0@FBGA105 [DX5056]
PF38F6070M0Y0B0@FBGA105 [DX5056]
PF38F6070M0Y0BE@FBGA105 [DX5056]
PF38F6070M0Y0VE@FBGA165 [DX5120]
PF38F6070M0Y0VF@FBGA165 [DX5120]
PF38F6070M0Y1CE@FBGA107 [DX50UN]
PF38F6070M0Y1VF@FBGA165 [DX50UN]
PF38F6080M0Y0VE@FBGA165 [DX5120]
PF38F6080M0Y1VE@FBGA165 [DX50UN]
PF48F3000M0Y0QE@FBGA88 [DX5005]
PF48F3000P0ZBQE@FBGA88 [DX5005]
PF48F3000P0ZTQE@FBGA88 [DX5005]
PF48F4000M0Y0CE@FBGA107 [DX5077]
PF48F4000P0ZBQE@FBGA88 [DX5001]
PF48F4000P0ZTQE@FBGA88 [DX5001]
PF48F4400P0VBQE@FBGA88 [DX5001]
PF48F5000M0Y0B0@FBGA105 [DX5077]
PF48F5000M0Y0BE@FBGA105 [DX5077]
PF48F5000M0Y0C0@FBGA107 [DX5077]
PF48F5000M0Y1B0@FBGA105 [DX5077]
PF48F5000M0Y1BE@FBGA105 [DX5077]
PF48F6000M0Y0BE@FBGA105 [DX5077]
PF48F6000M0Y0BF@FBGA105 [DX5077]
PF48F6000M0Y0BG@FBGA105 [DX5077]
PF48F6000M0Y0BH@FBGA105 [DX5077]
PF48F6000M0Y1BE@FBGA105 [DX5077]
PF48F6600M0U0BE@FBGA105 [DX5077]
PF48F6600M0U0BF@FBGA105 [DX5077]
PF48F6600M0U0BM@FBGA105 [DX5077]
PF58F0026M0Y1BE@FBGA105 [DX5056]
PF58F0042M0Y0WE@FBGA165 [DX5101]
PF58F0048M0Y0WE@FBGA165 [DX5101]
PF58F0051M0Y1WE@FBGA165 [DX5109]
PF58F0051M0Y1WF@FBGA165 [DX5109]
PF58F0051M0Y1WG@FBGA165 [DX5109]
PF58F0051M0Y1WH@FBGA165 [DX5108]
PF58F0051M0Y1WJ@FBGA165 [DX5108]
PF58F0051M0Y1WK@FBGA165 [DX5108]
PF58F0058M0Y1WE@FBGA165 [DX5108]
PF58F0062M0Y1BF@FBGA105 [DX5056]
PF58F0062M0Y1BG@FBGA105 [DX5056]
PF58F0067M0Y0WE@FBGA165 [DX50UN]
PF58F0067M0Y0WF@FBGA165 [DX5101]
PF58F0068M0Y0WE@FBGA165 [DX5101]
PF58F0071M0Y0WE@FBGA165 [DX5101]
PF58F0073M0Y1WE@FBGA165 [DX5108]
PF58F0075M0Y1WE@FBGA165 [DX5108]
PZ28F032M29EWB@FBGA48 [DX5002]
PZ28F032M29EWH@FBGA48 [DX5002]
PZ28F032M29EWL@FBGA48 [DX5002]
PZ28F032M29EWT@FBGA48 [DX5002]
PZ28F064M29EWB@FBGA48 [DX5002]
PZ28F064M29EWH@FBGA48 [DX5002]
PZ28F064M29EWL@FBGA48 [DX5002]
PZ28F064M29EWT@FBGA48 [DX5002]
RC28F00BM29EWH@FBGA64 [DX5074]
RC28F128J3F@FBGA64 [DX5004]
RC28F128M29EWH@FBGA64 [DX5074]
RC28F128M29EWL@FBGA64 [DX5074]
RC28F128P30BF@FBGA64 [DX5004]
RC28F128P30TF@FBGA64 [DX5004]

RC28F128P33BF@FBGA64 [DX5019]
RC28F128P33TF@FBGA64 [DX5019]
RC28F256J3F@FBGA64 [DX5004]
RC28F256M29EWH@FBGA64 [DX5074]
RC28F256M29EWHS@FBGA64 [DX5074]
RC28F256M29EWL@FBGA64 [DX5074]
RC28F256M29EWLS@FBGA64 [DX5074]
RC28F256P30BF@FBGA64 [DX5004]
RC28F256P30TF@FBGA64 [DX5004]
RC28F256P33BF@FBGA64 [DX5004]
RC28F256P33TF@FBGA64 [DX5004]
RC28F320J3F@FBGA64 [DX5004]
RC28F512M29EWH@FBGA64 [DX5074]
RC28F512M29EWHS@FBGA64 [DX5074]
RC28F512M29EWL@FBGA64 [DX5074]
RC28F512M29EWLS@FBGA64 [DX5074]
RC28F640J3F@FBGA64 [DX5004]
RC28F640P30BF@FBGA64 [DX5004]
RC28F640P30TF@FBGA64 [DX5004]
RC28F640P33BF@FBGA64 [DX5019]
RC28F640P33TF@FBGA64 [DX5019]
RC48F4400P0TB0E@FBGA64 [DX5004]
RC48F4400P0VB0E@FBGA64 [DX5004]
RD38F4460LVYBB0@FBGA103 [DX5056]
RD38F4460LVYGB0@FBGA103 [DX5056]
RD38F4460LVYTB0@FBGA103 [DX5056]
RD38F5070L0Y3AE@FBGA64 [DX5127]
RD48F3000P0ZBQE@FBGA88 [DX5005]
RD48F3000P0ZTQE@FBGA88 [DX5005]
RD48F4400L0ZDN0@FBGA88 [DX5001]
RD48F4440LVYBQ0@FBGA88 [DX5001]
RD48F4444LLZBB0@FBGA103 [DX50UN]
RD48F4444LVYBB0@FBGA103 [DX50UN]
RF48F4400P0VBQE@FBGA88 [DX5001]
TE28F128J3F@TSOP56 [DX1011]
TE28F128P30BF@TSOP56 [DX1011]
TE28F128P30TF@TSOP56 [DX1011]
TE28F128P33BF@TSOP56 [DX1011]
TE28F128P33TF@TSOP56 [DX1011]
TE28F256J3F@TSOP56 [DX1011]
TE28F256P30BF@TSOP56 [DX1011]
TE28F256P30TF@TSOP56 [DX1011]
TE28F256P33BF@TSOP56 [DX1011]
TE28F256P33TF@TSOP56 [DX1011]
TE28F320J3F@TSOP56 [DX1011]
TE28F640J3F@TSOP56 [DX1011]

NUVOTON

MICROCONTROLLER

M0516LAN@QFP48 [DX3007]
M0516LBN@QFP48 [DX3007]
M0516LDE@QFP48 [DX3007]
M0516LDN@QFP48 [DX3007]
M0516ZAN@QFN32 [DX4015]
M0516ZBN@QFN32 [DX4015]
M0516ZDE@QF33 [DX4015]
M0516ZDN@QF33 [DX4015]
M0518LC2AE@QFP48 [DX3007]
M0518LD2AE@QFP48 [DX3007]
M0518SC2AE@QFP64 [DX3085]
M0518SD2AE@QFP64 [DX3085]
M0519SD3AE@QFP64 [DX3085]
M0519SE3AE@QFP64 [DX3085]
M0519VE3AE@QFP100 [DX3021]
M052LAN@QFP48 [DX3007]
M052LBN@QFP48 [DX3007]
M052LDE@QFP48 [DX3007]
M052LDN@QFP48 [DX3007]
M052ZAN@QFN32 [DX4015]
M052ZBN@QFN32 [DX4015]
M052ZDE@QF33 [DX4015]
M052ZDN@QF33 [DX4015]
M054LAN@QFP48 [DX3007]
M054LBN@QFP48 [DX3007]
M054LDE@QFP48 [DX3007]
M054LDN@QFP48 [DX3007]
M054ZAN@QFN32 [DX4015]
M054ZBN@QFN32 [DX4015]
M054ZDE@QF33 [DX4015]
M054ZDN@QF33 [DX4015]
M058LAN@QFP48 [DX3007]
M058LBN@QFP48 [DX3007]
M058LDE@QFP48 [DX3007]
M058LDN@QFP48 [DX3007]
M058SFAN(ICP)@TSSOP20 [DX1001]
M058SLAN(ICP)@QFP48 [DX3007]
M058SLAN@QFP48 [DX3007]

M058SSAN(ICP)@QFP64 [DX3085]
M058SSAN@QFP64 [DX3085]
M058SZAN(ICP)@QFN33 [DX4015]
M058SZAN@QF33 [DX4015]
M058ZAN@QFN32 [DX4015]
M058ZBN@QFN32 [DX4015]
M058ZDE@QF33 [DX4015]
M058ZDN@QF33 [DX4015]
M451LC3AE@QFP48 [DX3007]
M451LD3AE@QFP48 [DX3007]
M451LE6AE@QFP48 [DX3007]
M451LG6AE@QFP48 [DX3007]
M451MLC3AE@QFP48 [DX3007]
M451MLD3AE@QFP48 [DX3007]
M451MLE6AE@QFP48 [DX3007]
M451MLG6AE@QFP48 [DX3007]
M451MSC3AE@QFP64 [DX3085]
M451MSD3AE@QFP64 [DX3085]
M451RC3AE@QFP64 [DX3011]
M451RD3AE@QFP64 [DX3011]
M451RE6AE@QFP64 [DX3011]
M451RG6AE@QFP64 [DX3011]
M451VE6AE@QFP100 [DX3021]
M451VG6AE@QFP100 [DX3021]
M452LC3AE@QFP48 [DX3007]
M452LD3AE@QFP48 [DX3007]
M452LE6AE@QFP48 [DX3007]
M452LG6AE@QFP48 [DX3007]
M452RD3AE@QFP64 [DX3011]
M452RE6AE@QFP64 [DX3011]
M452RG6AE@QFP64 [DX3011]
M453LC3AE@QFP48 [DX3007]
M453LD3AE@QFP48 [DX3007]
M453LE6AE@QFP48 [DX3007]
M453LG6AE@QFP48 [DX3007]
M453RD3AE@QFP64 [DX3011]
M453RE6AE@QFP64 [DX3011]
M453RG6AE@QFP64 [DX3011]
M453VD3AE@QFP100 [DX3021]
M453VE6AE@QFP100 [DX3021]
M453VG6AE@QFP100 [DX3021]
MINI51FDE(ICP)@TSSOP20 [DX1001]
MINI51LAN@QFN33 [DX4015]
MINI51LAN@QFP48 [DX3007]
MINI51LDE(ICP)@QFP48 [DX3007]
MINI51LDE@QFP48 [DX3007]
MINI51TDE(ICP)@QFN33 [DX4084]
MINI51TDE@QFN33 [DX4084]
MINI51ZDE(ICP)@QFN33 [DX4015]
MINI51ZDE@QFN33 [DX4015]
MINI52FDE(ICP)@TSSOP20 [DX1001]
MINI52LAN@QFN33 [DX4015]
MINI52LAN@QFP48 [DX3007]
MINI52LDE(ICP)@QFP48 [DX3007]
MINI52LDE@QFP48 [DX3007]
MINI52TDE(ICP)@QFN33 [DX4084]
MINI52TDE@QFN33 [DX4084]
MINI52ZDE(ICP)@QFN33 [DX4015]
MINI52ZDE@QFN33 [DX4015]
MINI54FDE(ICP)@TSSOP20 [DX1001]
MINI54LAN@QFN33 [DX4015]
MINI54LAN@QFP48 [DX3007]
MINI54LDE(ICP)@QFP48 [DX3007]
MINI54LDE@QFP48 [DX3007]
MINI54TDE(ICP)@QFN33 [DX4084]
MINI54TDE@QFN33 [DX4084]
MINI54ZDE(ICP)@QFN33 [DX4015]
MINI54ZDE@QFN33 [DX4015]
MINI58FDE(ICP)@TSSOP20 [DX1001]
MINI58LDE(ICP)@QFP48 [DX3007]
MINI58LDE@QFP48 [DX3007]
MINI58TDE(ICP)@QFN33 [DX4084]
MINI58TDE@QFN33 [DX4084]
MINI58ZDE(ICP)@QFN33 [DX4015]
MINI58ZDE@QFN33 [DX4015]
N76E616A@LQFP48 [DX3007]
N76E885A@TSSOP20 [DX1001]
N76E885A@TSSOP28 [DX1001]
N78E055ADG [DX0001]
N78E055AFG@TQFP44 [DX3002]
N78E055ALG@TQFP48 [DX3007]
N78E055APG@PLCC44 [DX2044]
N78E059ADG [DX0001]
N78E059AFG@TQFP44 [DX3002]
N78E059ALG@TQFP48 [DX3007]
N78E059APG@PLCC44 [DX2044]
N78E366ADG [DX0001]
N78E366AFG@PQFP44 [DX3002]
N78E366ALG@LQFP48 [DX3007]
N78E366APG@PLCC44 [DX2044]
N78E517ADG [DX0001]
N78E517AFG@PQFP44 [DX3002]
N78E517ALG@LQFP48 [DX3007]
N78E517APG@PLCC44 [DX2044]
N79E234ALG@TQFP48 [DX3007]
N79E234RALG@TQFP48 [DX3007]

N79E235ALG@TQFP48 [DX3007]
N79E235RALG@TQFP48 [DX3007]
N79E342AKG [DX0001]
N79E342ASG@SOP16 [DX1033]
N79E342RAKG [DX0001]
N79E342RASG@SOP16 [DX1033]
N79E352AEG [DX0001]
N79E352AFG@TQFP44 [DX3002]
N79E352ALG@TQFP48 [DX3007]
N79E352APG@PLCC44 [DX2044]
N79E8132A@SSOP16 [DX0001]
N79E813A [DX0001]
N79E813A@SOIC20 [DX1033]
N79E813A@SOIC28 [DX1033]
N79E813A@TSSOP20 [DX1067]
N79E813A@TSSOP28 [DX1001]
N79E814A [DX0001]
N79E814A(ICP) [DX0001]
N79E814A(ICP)@SOIC20 [DX1033]
N79E814A(ICP)@SOIC28 [DX1033]
N79E814A(ICP)@TSSOP20 [DX1000]
N79E814A(ICP)@TSSOP28 [DX1001]
N79E814A@SOIC20 [DX1033]
N79E814A@SOIC28 [DX1033]
N79E814A@TSSOP20 [DX1067]
N79E814A@TSSOP28 [DX1001]
N79E815A [DX0001]
N79E815A(ICP) [DX0001]
N79E815A(ICP)@SOIC20 [DX1033]
N79E815A(ICP)@SOIC28 [DX1033]
N79E815A(ICP)@TSSOP20 [DX1000]
N79E815A(ICP)@TSSOP28 [DX1001]
N79E815A@SOIC20 [DX1033]
N79E815A@SOIC28 [DX1033]
N79E815A@TSSOP20 [DX1067]
N79E815A@TSSOP28 [DX1001]
N79E8213AKG [DX0001]
N79E8213ASG@SOP20 [DX1033]
N79E8213RAKG [DX0001]
N79E8213RASG@SOP20 [DX1033]
N79E822A [DX0001]
N79E822A@SOP20 [DX1033]
N79E823A [DX0001]
N79E823A@SOP20 [DX1033]
N79E824A [DX0001]
N79E824A@SOP20 [DX1033]
N79E825A [DX0001]
N79E825A@SOP20 [DX1033]
N79E8432A@SSOP16 [DX0001]
N79E843A [DX0001]
N79E843A@SOIC20 [DX1033]
N79E843A@TSSOP20 [DX1067]
N79E844A [DX0001]
N79E844A@SOIC20 [DX1033]
N79E844A@TSSOP20 [DX1067]
N79E845A [DX0001]
N79E845A@SOIC20 [DX1033]
N79E845A@TSSOP20 [DX1067]
N79E853A@SOIC28 [DX1033]
N79E853A@TSSOP28 [DX1000]
N79E854A@SOIC28 [DX1033]
N79E854A@TSSOP28 [DX1000]
N79E855A@SOIC28 [DX1033]
N79E855A@TSSOP28 [DX1000]
N79E875ALG@TQFP48 [DX3007]
N79E875RALG@TQFP48 [DX3007]
NANO100KC2BN@LQFP128 [DX3030]
NANO100KD2BN@LQFP128 [DX3030]
NANO100KD3BN@LQFP128 [DX3030]
NANO100KE2BN@LQFP128 [DX3030]
NANO100KE3BN@LQFP128 [DX3030]
NANO100LC2AN@LQFP48 [DX3007]
NANO100LC2BN@LQFP48 [DX3007]
NANO100LD2AN@LQFP48 [DX3007]
NANO100LD2BN@LQFP48 [DX3007]
NANO100LD3AN@LQFP48 [DX3007]
NANO100LD3BN@LQFP48 [DX3007]
NANO100LE2BN@LQFP48 [DX3007]
NANO100LE3BN@LQFP48 [DX3007]
NANO100NC2BN@QFN48 [DX4021]
NANO100ND2BN@QFN48 [DX4021]
NANO100NE3BN@QFN48 [DX4021]
NANO100SC2AN@LQFP64 [DX3085]
NANO100SC2BN@LQFP64 [DX3085]
NANO100SD2AN@LQFP64 [DX3085]
NANO100SD2BN@LQFP64 [DX3085]
NANO100SD3AN@LQFP64 [DX3085]
NANO100SD3BN@LQFP64 [DX3085]
NANO100SE2BN@LQFP64 [DX3085]
NANO100SE3BN@LQFP64 [DX3085]
NANO100VD2AN@LQFP100 [DX3021]
NANO100VD3AN@LQFP100 [DX3021]
NANO102LB0AN@LQFP48 [DX3007]
NANO102LB1AN@LQFP48 [DX3007]
NANO102LC1AN@LQFP48 [DX3007]
NANO102LC2AN@LQFP48 [DX3007]

NANO102SB0AN@LQFP64 [DX3085]
NANO102SB1AN@LQFP64 [DX3085]
NANO102SC1AN@LQFP64 [DX3085]
NANO102SC2AN@LQFP64 [DX3085]
NANO102ZB0AN@QFN33 [DX4015]
NANO102ZB1AN@QFN33 [DX4015]
NANO102ZC1AN@QFN33 [DX4015]
NANO102ZC2AN@QFN33 [DX4015]
NANO110KC2BN@LQFP128 [DX3030]
NANO110KD2BN@LQFP128 [DX3030]
NANO110KD3BN@LQFP128 [DX3030]
NANO110KE2BN@LQFP128 [DX3030]
NANO110KE3BN@LQFP128 [DX3030]
NANO110RC2BN@LQFP64 [DX3011]
NANO110SC2AN@LQFP64 [DX3085]
NANO110SC2BN@LQFP64 [DX3085]
NANO110SD2AN@LQFP64 [DX3085]
NANO110SD2BN@LQFP64 [DX3085]
NANO110SD3AN@LQFP64 [DX3085]
NANO110SD3BN@LQFP64 [DX3085]
NANO110SE2BN@LQFP64 [DX3085]
NANO110SE3BN@LQFP64 [DX3085]
NANO110VD2AN@LQFP100 [DX3021]
NANO110VD3AN@LQFP100 [DX3021]
NANO112LB0AN@LQFP48 [DX3007]
NANO112LB1AN@LQFP48 [DX3007]
NANO112LC1AN@LQFP48 [DX3007]
NANO112LC2AN@LQFP48 [DX3007]
NANO112RB0AN@LQFP64 [DX3011]
NANO112RB1AN@LQFP64 [DX3011]
NANO112RC1AN@LQFP64 [DX3011]
NANO112RC2AN@LQFP64 [DX3011]
NANO112SB0AN@LQFP64 [DX3085]
NANO112SB1AN@LQFP64 [DX3085]
NANO112SC1AN@LQFP64 [DX3085]
NANO112SC2AN@LQFP64 [DX3085]
NANO112VB0AN@LQFP100 [DX3021]
NANO112VB1AN@LQFP100 [DX3021]
NANO112VC1AN@LQFP100 [DX3021]
NANO112VC2AN@LQFP100 [DX3021]
NANO120KC2BN@LQFP128 [DX3030]
NANO120KD2BN@LQFP128 [DX3030]
NANO120KD3BN@LQFP128 [DX3030]
NANO120KE2BN@LQFP128 [DX3030]
NANO120KE3BN@LQFP128 [DX3030]
NANO120LC2AN@LQFP48 [DX3007]
NANO120LC2BN@LQFP48 [DX3007]
NANO120LD2AN@LQFP48 [DX3007]
NANO120LD2BN@LQFP48 [DX3007]
NANO120LD3AN@LQFP48 [DX3007]
NANO120LD3BN@LQFP48 [DX3007]
NANO120LE2BN@LQFP48 [DX3007]
NANO120LE3BN@LQFP48 [DX3007]
NANO120SC2AN@LQFP64 [DX3085]
NANO120SC2BN@LQFP64 [DX3085]
NANO120SD2AN@LQFP64 [DX3085]
NANO120SD2BN@LQFP64 [DX3085]
NANO120SD3AN@LQFP64 [DX3085]
NANO120SD3BN@LQFP64 [DX3085]
NANO120SE2BN@LQFP64 [DX3085]
NANO120SE3BN@LQFP64 [DX3085]
NANO120VD2AN@LQFP100 [DX3021]
NANO120VD3AN@LQFP100 [DX3021]
NANO130KC2BN@LQFP128 [DX3030]
NANO130KD2BN@LQFP128 [DX3030]
NANO130KD3BN@LQFP128 [DX3030]
NANO130KE2BN@LQFP128 [DX3030]
NANO130KE3BN@LQFP128 [DX3030]
NANO130SC2BN@LQFP64 [DX3085]
NANO130SD2BN@LQFP64 [DX3085]
NANO130SD3BN@LQFP64 [DX3085]
NANO130SE2BN@LQFP64 [DX3085]
NANO130SE3BN@LQFP64 [DX3085]
NANO130VC2AN@LQFP100 [DX3021]
NANO130VD2AN@LQFP100 [DX3021]
NANO130VD3AN@LQFP100 [DX3021]
NPCE698L@LQFP64 [DX3085]
NPCE948U@LQFP64 [DX3085]
NUC029LAN(ICP)@LQFP48 [DX3007]
NUC029LAN@LQFP48 [DX3007]
NUC029TAN(ICP)@QFN33 [DX4084]
NUC029TAN@QFN33 [DX3007]
NUC100LC1AN@LQFP48 [DX3007]
NUC100LC1BN@LQFP48 [DX3007]
NUC100LC1CN@LQFP48 [DX3007]
NUC100LC1DN@LQFP48 [DX3007]
NUC100LD1AN@LQFP48 [DX3007]
NUC100LD1BN@LQFP48 [DX3007]
NUC100LD1CN@LQFP48 [DX3007]
NUC100LD1DN@LQFP48 [DX3007]
NUC100LD2AN@LQFP48 [DX3007]
NUC100LD2BN@LQFP48 [DX3007]
NUC100LD2CN@LQFP48 [DX3007]
NUC100LD2DN@LQFP48 [DX3007]
NUC100LD3AN@LQFP48 [DX3007]
NUC100LD3CN@LQFP48 [DX3007]

NUC100LD3DN@LQFP48 [DX3007]
NUC100LE3AN@LQFP48 [DX3007]
NUC100LE3CN@LQFP48 [DX3007]
NUC100LE3DN@LQFP48 [DX3007]
NUC100RC1AN@LQFP64 [DX3011]
NUC100RC1BN@LQFP64 [DX3011]
NUC100RC1CN@LQFP64 [DX3011]
NUC100RC1DN@LQFP64 [DX3011]
NUC100RD1AN@LQFP64 [DX3011]
NUC100RD1BN@LQFP64 [DX3011]
NUC100RD1CN@LQFP64 [DX3011]
NUC100RD1DN@LQFP64 [DX3011]
NUC100RD2AN@LQFP64 [DX3011]
NUC100RD2BN@LQFP64 [DX3011]
NUC100RD2CN@LQFP64 [DX3011]
NUC100RD2DN@LQFP64 [DX3011]
NUC100RD3AN@LQFP64 [DX3011]
NUC100RD3CN@LQFP64 [DX3011]
NUC100RD3DN@LQFP64 [DX3011]
NUC100RE3AN@LQFP64 [DX3011]
NUC100RE3CN@LQFP64 [DX3011]
NUC100RE3DN@LQFP64 [DX3011]
NUC100VD2AN@LQFP100 [DX3021]
NUC100VD2CN@LQFP100 [DX3021]
NUC100VD2DN@LQFP100 [DX3021]
NUC100VD3AN@LQFP100 [DX3021]
NUC100VD3CN@LQFP100 [DX3021]
NUC100VD3DN@LQFP100 [DX3021]
NUC100VE3AN@LQFP100 [DX3021]
NUC100VE3CN@LQFP100 [DX3021]
NUC100VE3DN@LQFP100 [DX3021]
NUC102LC1AN@QFP48 [DX3007]
NUC102LD2AN@QFP48 [DX3007]
NUC102YC1AN@QFN36 [DX4029]
NUC102YD2AN@QFN36 [DX4029]
NUC102ZC1AN@QFN33 [DX4015]
NUC102ZC2AN@QFN33 [DX4015]
NUC102ZD2AN@QFN33 [DX4015]
NUC120LC1AN@LQFP48 [DX3007]
NUC120LC1BN@LQFP48 [DX3007]
NUC120LC1CN@LQFP48 [DX3007]
NUC120LC1DN@LQFP48 [DX3007]
NUC120LD1AN@LQFP48 [DX3007]
NUC120LD1BN@LQFP48 [DX3007]
NUC120LD1CN@LQFP48 [DX3007]
NUC120LD1DN@LQFP48 [DX3007]
NUC120LD2AN@LQFP48 [DX3007]
NUC120LD2BN@LQFP48 [DX3007]
NUC120LD2CN@LQFP48 [DX3007]
NUC120LD2DN@LQFP48 [DX3007]
NUC120LD3AN@LQFP48 [DX3007]
NUC120LD3CN@LQFP48 [DX3007]
NUC120LD3DN@LQFP48 [DX3007]
NUC120LE3AN@LQFP48 [DX3007]
NUC120LE3CN@LQFP48 [DX3007]
NUC120LE3DN@LQFP48 [DX3007]
NUC120RC1AN@LQFP64 [DX3011]
NUC120RC1BN@LQFP64 [DX3011]
NUC120RC1CN@LQFP64 [DX3011]
NUC120RC1DN@LQFP64 [DX3011]
NUC120RD1AN@LQFP64 [DX3011]
NUC120RD1BN@LQFP64 [DX3011]
NUC120RD1CN@LQFP64 [DX3011]
NUC120RD1DN@LQFP64 [DX3011]
NUC120RD2AN@LQFP64 [DX3011]
NUC120RD2BN@LQFP64 [DX3011]
NUC120RD2CN@LQFP64 [DX3011]
NUC120RD2DN@LQFP64 [DX3011]
NUC120RD3AN@LQFP64 [DX3011]
NUC120RD3CN@LQFP64 [DX3011]
NUC120RD3DN@LQFP64 [DX3011]
NUC120RE3AN@LQFP64 [DX3011]
NUC120RE3CN@LQFP64 [DX3011]
NUC120RE3DN@LQFP64 [DX3011]
NUC120VD2AN@LQFP100 [DX3021]
NUC120VD2CN@LQFP100 [DX3021]
NUC120VD2DN@LQFP100 [DX3021]
NUC120VD3AN@LQFP100 [DX3021]
NUC120VD3CN@LQFP100 [DX3021]
NUC120VD3DN@LQFP100 [DX3021]
NUC120VE3AN@LQFP100 [DX3021]
NUC120VE3CN@LQFP100 [DX3021]
NUC120VE3DN@LQFP100 [DX3021]
NUC122LC1AN@QFP48 [DX3007]
NUC122LD2AN@QFP48 [DX3007]
NUC122SC1AN@QFP64 [DX3085]
NUC122SD2AN@QFP64 [DX3085]
NUC122SD2AN@QFP64(HW) [DX3085]
NUC122ZC1AN@QFN33 [DX4015]
NUC122ZD2AN@QFN33 [DX4015]
NUC123LC2AE1@QFP48 [DX3007]
NUC123LC2AN1@QFP48 [DX3007]
NUC123LD4AE0@QFP48 [DX3007]
NUC123LD4AN0@QFP48 [DX3007]
NUC123SC2AE1@QFP64 [DX3085]
NUC123SC2AN1@QFP64 [DX3085]

NUC123SD4AE0@QFP64 [DX3085]
NUC123SD4AN0@QFP64 [DX3085]
NUC123ZC2AE1@QFN33 [DX4015]
NUC123ZC2AN1@QFN33 [DX4015]
NUC123ZD4AE0@QFN33 [DX4015]
NUC123ZD4AN0@QFN33 [DX4015]
NUC130LC1CN@LQFP48 [DX3007]
NUC130LD2AN@LQFP48 [DX3007]
NUC130LD2CN@LQFP48 [DX3007]
NUC130LD3AN@LQFP48 [DX3007]
NUC130LE3AN@LQFP48 [DX3007]
NUC130LE3CN@LQFP48 [DX3007]
NUC130RC1CN@LQFP64 [DX3011]
NUC130RD2AN@LQFP64 [DX3011]
NUC130RD2CN@LQFP64 [DX3011]
NUC130RD3AN@LQFP64 [DX3011]
NUC130RE3AN@LQFP64 [DX3011]
NUC130RE3CN@LQFP64 [DX3011]
NUC130VD2AN@LQFP100 [DX3021]
NUC130VD3AN@LQFP100 [DX3021]
NUC130VE3AN@LQFP100 [DX3021]
NUC130VE3CN@LQFP100 [DX3021]
NUC131LC2AE@LQFP48 [DX3007]
NUC131LD2AE@LQFP48 [DX3007]
NUC131RC1AE@LQFP64 [DX3011]
NUC131SC2AE@LQFP64 [DX3085]
NUC131SD2AE@LQFP64 [DX3085]
NUC140LC1CN@LQFP48 [DX3007]
NUC140LD2AN@LQFP48 [DX3007]
NUC140LD2CN@LQFP48 [DX3007]
NUC140LD3AN@LQFP48 [DX3007]
NUC140LE3AN@LQFP48 [DX3007]
NUC140LE3CN@LQFP48 [DX3007]
NUC140RC1CN@LQFP64 [DX3011]
NUC140RD2AN@LQFP64 [DX3011]
NUC140RD2CN@LQFP64 [DX3011]
NUC140RD3AN@LQFP64 [DX3011]
NUC140RE3AN@LQFP64 [DX3011]
NUC140RE3CN@LQFP64 [DX3011]
NUC140VD2AN@LQFP100 [DX3021]
NUC140VD3AN@LQFP100 [DX3021]
NUC140VE3AN@LQFP100 [DX3021]
NUC140VE3CN@LQFP100 [DX3021]
NUC200LC2AE@LQFP48 [DX3007]
NUC200LC2AN@LQFP48 [DX3007]
NUC200LD2AE@LQFP48 [DX3007]
NUC200LD2AN@LQFP48 [DX3007]
NUC200LE3AE@LQFP48 [DX3007]
NUC200LE3AN@LQFP48 [DX3007]
NUC200SC2AE@LQFP64 [DX3011]
NUC200SC2AN@LQFP64 [DX3011]
NUC200SD2AE@LQFP64 [DX3011]
NUC200SD2AN@LQFP64 [DX3011]
NUC200SE3AE@LQFP64 [DX3011]
NUC200SE3AN@LQFP64 [DX3011]
NUC200VE3AE@LQFP100 [DX3021]
NUC200VE3AN@LQFP100 [DX3021]
NUC220LC2AE@LQFP48 [DX3007]
NUC220LC2AN@LQFP48 [DX3007]
NUC220LD2AE@LQFP48 [DX3007]
NUC220LD2AN@LQFP48 [DX3007]
NUC220LE3AE@LQFP48 [DX3007]
NUC220LE3AN@LQFP48 [DX3007]
NUC220SC2AE@LQFP64 [DX3011]
NUC220SC2AN@LQFP64 [DX3011]
NUC220SD2AE@LQFP64 [DX3011]
NUC220SD2AN@LQFP64 [DX3011]
NUC220SE3AE@LQFP64 [DX3011]
NUC220SE3AN@LQFP64 [DX3011]
NUC220VE3AE@LQFP100 [DX3021]
NUC220VE3AN@LQFP100 [DX3021]
NUC230LC2AE@QFP48 [DX3007]
NUC230LC2AN@QFP48 [DX3007]
NUC230LD2AE@QFP48 [DX3007]
NUC230LD2AN@QFP48 [DX3007]
NUC230LE3AE@QFP48 [DX3007]
NUC230LE3AN@QFP48 [DX3007]
NUC230RC1AE@QFP64 [DX3011]
NUC230SC2AE@QFP64 [DX3011]
NUC230SC2AN@QFP64 [DX3011]
NUC230SD2AE@QFP64 [DX3011]
NUC230SD2AN@QFP64 [DX3011]
NUC230SE3AE@QFP64 [DX3011]
NUC230SE3AN@QFP64 [DX3011]
NUC230VE3AE@QFP100 [DX3021]
NUC230VE3AN@QFP100 [DX3021]
NUC240LC2AE@QFP48 [DX3007]
NUC240LC2AN@QFP48 [DX3007]
NUC240LD2AE@QFP48 [DX3007]
NUC240LD2AN@QFP48 [DX3007]
NUC240LE3AE@QFP48 [DX3007]
NUC240LE3AN@QFP48 [DX3007]
NUC240SC2AE@QFP64 [DX3011]
NUC240SC2AN@QFP64 [DX3011]
NUC240SD2AE@QFP64 [DX3011]
NUC240SD2AN@QFP64 [DX3011]

NUC240SE3AE@QFP64 [DX3011]
NUC240SE3AN@QFP64 [DX3011]
NUC240VE3AE@QFP100 [DX3021]
NUC240VE3AN@QFP100 [DX3021]
W77E058A [DX0001]
W77E058A@PLCC44 [DX2044]
W77E058A@TQFP44 [DX3002]
W77E468@QFP100 [DX3023]
W77E516 [DX0001]
W77E516@PLCC44 [DX2044]
W77E516@TQFP44 [DX3002]
W77E532 [DX0001]
W77E532@PLCC44 [DX2044]
W77E532@TQFP44 [DX3002]
W77E532A [DX0001]
W77E532A@PLCC44 [DX2044]
W77E532A@TQFP44 [DX3002]
W77E58 [DX0001]
W77E58@PLCC44 [DX2044]
W77E58@TQFP44 [DX3002]
W77IE58 [DX0001]
W77IE58@PLCC44 [DX2044]
W77IE58@TQFP44 [DX3002]
W77L058A [DX0001]
W77L058A@PLCC44 [DX2044]
W77L058A@TQFP44 [DX3002]
W77L516A [DX0001]
W77L516A@PLCC44 [DX2044]
W77L516A@TQFP44 [DX3002]
W77L532A [DX0001]
W77L532A@PLCC44 [DX2044]
W77L532A@TQFP44 [DX3002]
W77LE516 [DX0001]
W77LE516@PLCC44 [DX2044]
W77LE516@TQFP44 [DX3002]
W77LE532 [DX0001]
W77LE532@PLCC44 [DX2044]
W77LE532@TQFP44 [DX3002]
W77LE58 [DX0001]
W77LE58@PLCC44 [DX2044]
W77LE58@TQFP44 [DX3002]
W77LE58A [DX0001]
W77LE58A@PLCC44 [DX2044]
W77LE58A@TQFP44 [DX3002]
W78E051B [DX0001]
W78E051B@PLCC44 [DX2044]
W78E051B@TQFP44 [DX3002]
W78E051C [DX0001]
W78E051C@PLCC44 [DX2044]
W78E051C@TQFP44 [DX3002]
W78E051DDG [DX0001]
W78E051DFG@PQFP44 [DX3002]
W78E051DLG@LQFP48 [DX3007]
W78E051DPG@PLCC44 [DX2044]
W78E052B [DX0001]
W78E052B@PLCC44 [DX2044]
W78E052B@TQFP44 [DX3002]
W78E052C [DX0001]
W78E052C@PLCC44 [DX2044]
W78E052C@TQFP44 [DX3002]
W78E052DDG [DX0001]
W78E052DFG@PQFP44 [DX3002]
W78E052DLG@LQFP48 [DX3007]
W78E052DPG@PLCC44 [DX2044]
W78E054B [DX0001]
W78E054B@PLCC44 [DX2044]
W78E054B@TQFP44 [DX3002]
W78E054C [DX0001]
W78E054C@PLCC44 [DX2044]
W78E054C@TQFP44 [DX3002]
W78E054DDG [DX0001]
W78E054DFG@PQFP44 [DX3002]
W78E054DLG@LQFP48 [DX3007]
W78E054DPG@PLCC44 [DX2044]
W78E058B [DX0001]
W78E058B@PLCC44 [DX2044]
W78E058B@TQFP44 [DX3002]
W78E058DDG [DX0001]
W78E058DFG@TQFP44 [DX3002]
W78E058DLG@TQFP48 [DX3007]
W78E058DPG@PLCC44 [DX2044]
W78E065 [DX0001]
W78E065@PLCC44 [DX2044]
W78E065@TQFP44 [DX3002]
W78E354(dip40) [DX0001]
W78E354(dip48) [DX0001]
W78E354@PLCC68 [DX2068]
W78E365 [DX0001]
W78E365@PLCC44 [DX2044]
W78E365@TQFP44 [DX3002]
W78E365A [DX0001]
W78E365A@PLCC44 [DX2044]
W78E365A@TQFP44 [DX3002]
W78E374B [DX0001]
W78E378 [DX0001]
W78E378E [DX0001]

W78E378P@PLCC44 [DX2044]
W78E51@PLCC44 [DX2044]
W78E516 [DX0001]
W78E516@TQFP44 [DX3002]
W78E516B@PLCC44 [DX2044]
W78E516DDG [DX0001]
W78E516DLG@TQFP48 [DX3007]
W78E51B [DX0001]
W78E51B@PQFP44 [DX3002]
W78E51C [DX0001]
W78E51C@TQFP44 [DX3002]
W78E52@PLCC44 [DX2044]
W78E52B [DX0001]
W78E52B@TQFP44 [DX3002]
W78E52C@PLCC44 [DX2044]
W78E54 [DX0001]
W78E54@PQFP44 [DX3002]
W78E54B [DX0001]
W78E54B@TQFP44 [DX3002]
W78E54C@PLCC44 [DX2044]
W78E58 [DX0001]
W78E58@PQFP44 [DX3002]
W78E58B [DX0001]
W78E58B@TQFP44 [DX3002]
W78E62B@PLCC44 [DX2044]
W78E65 [DX0001]
W78E65@TQFP44 [DX3002]
W78E858@PLCC44 [DX2044]
W78ERD2 [DX0001]
W78ERD2@TQFP44 [DX3002]
W78I051DFG@PQFP44 [DX3002]
W78I051DPG@PLCC44 [DX2044]
W78I052@PLCC44 [DX2044]
W78I052DFG@PQFP44 [DX3002]
W78I052DPG@PLCC44 [DX2044]
W78I054@PLCC44 [DX2044]
W78I054DFG@PQFP44 [DX3002]
W78I054DPG@PLCC44 [DX2044]
W78IE52@PLCC44 [DX2044]
W78IE54@PLCC44 [DX2044]
W78IRD2@PLCC44 [DX2044]
W78L051A [DX0001]
W78L051A@TQFP44 [DX3002]
W78L051C@PLCC44 [DX2044]
W78L052A [DX0001]
W78L052A@TQFP44 [DX3002]
W78L052C@PLCC44 [DX2044]
W78L054A [DX0001]
W78E51 [DX0001]
W78E51@TQFP44 [DX3002]
W78E516@PLCC44 [DX2044]
W78E516B [DX0001]
W78E516B@TQFP44 [DX3002]
W78E516DFG@TQFP44 [DX3002]
W78E516DPG@PLCC44 [DX2044]
W78E51B@PLCC44 [DX2044]
W78E51B@TQFP44 [DX3003]
W78E51C@PLCC44 [DX2044]
W78E52 [DX0001]
W78E52@TQFP44 [DX3002]
W78E52B@PLCC44 [DX2044]
W78E52C [DX0001]
W78E52C@TQFP44 [DX3002]
W78E54@PLCC44 [DX2044]
W78E54@TQFP44 [DX3003]
W78E54B@PLCC44 [DX2044]
W78E54C [DX0001]
W78E54C@TQFP44 [DX3002]
W78E58@PLCC44 [DX2044]
W78E58@TQFP44 [DX3003]
W78E58B@PLCC44 [DX2044]
W78E62B [DX0001]
W78E62B@TQFP44 [DX3002]
W78E65@PLCC44 [DX2044]
W78E858 [DX0001]
W78E858@TQFP44 [DX3002]
W78ERD2@PLCC44 [DX2044]
W78I051DDG [DX0001]
W78I051DLG@LQFP48 [DX3007]
W78I052 [DX0001]
W78I052DDG [DX0001]
W78I052DLG@LQFP48 [DX3007]
W78I054 [DX0001]
W78I054DDG [DX0001]
W78I054DLG@LQFP48 [DX3007]
W78IE52 [DX0001]
W78IE54 [DX0001]
W78IRD2 [DX0001]
W78IRD2@TQFP44 [DX3002]
W78L051A@PLCC44 [DX2044]
W78L051C [DX0001]
W78L051C@TQFP44 [DX3002]
W78L052A@PLCC44 [DX2044]
W78L052C [DX0001]
W78L052C@TQFP44 [DX3002]
W78L054A@PLCC44 [DX2044]

W78L054A@TQFP44 [DX3002]
W78L054C@PLCC44 [DX2044]
W78L058A [DX0001]
W78L058A@TQFP44 [DX3002]
W78L365@PLCC44 [DX2044]
W78L365@TQFP48 [DX3007]
W78L365A@PLCC44 [DX2044]
W78L365A@TQFP48 [DX3007]
W78L516@PLCC44 [DX2044]
W78L516A [DX0001]
W78L516A@TQFP44 [DX3002]
W78L812A@PLCC44 [DX2044]
W78LE365 [DX0001]
W78LE365@TQFP44 [DX3002]
W78LE51 [DX0001]
W78LE51@TQFP44 [DX3002]
W78LE516@PLCC44 [DX2044]
W78LE51C [DX0001]
W78LE51C@TQFP44 [DX3002]
W78LE52@PLCC44 [DX2044]
W78LE52C [DX0001]
W78LE52C@TQFP44 [DX3002]
W78LE54@PLCC44 [DX2044]
W78LE54C [DX0001]
W78LE54C@TQFP44 [DX3002]
W78LE58@PLCC44 [DX2044]
W78LE812 [DX0001]
W78LE812@TQFP44 [DX3002]
W79E201@TQFP44 [DX3002]
W79E2051(dip16) [DX0001]
W79E2051@SOIC14 [DX1033]
W79E2051@SOIC20 [DX1033]
W79E2051R@SOIC20 [DX1033]
W79E217AFG@PQFP100 [DX3023]
W79E225APG@PLCC44 [DX2044]
W79E226APG@PLCC44 [DX2044]
W79E227APG@PLCC44 [DX2044]
W79E4051(dip16) [DX0001]
W79E4051@SOIC14 [DX1033]
W79E4051@SOIC20 [DX1033]
W79E4051R@SOIC20 [DX1033]
W79E532@PLCC44 [DX2044]
W79E532A [DX0001]
W79E532A@TQFP44 [DX3002]
W79E632 [DX0001]
W79E632@TQFP44 [DX3002]
W79E632A@PLCC44 [DX2044]
W79E633A@PLCC44 [DX2044]
W78L054C [DX0001]
W78L054C@TQFP44 [DX3002]
W78L058A@PLCC44 [DX2044]
W78L365 [DX0001]
W78L365@TQFP44 [DX3002]
W78L365A [DX0001]
W78L365A@TQFP44 [DX3002]
W78L516 [DX0001]
W78L516@TQFP44 [DX3002]
W78L516A@PLCC44 [DX2044]
W78L812A [DX0001]
W78L812A@TQFP44 [DX3002]
W78LE365@PLCC44 [DX2044]
W78LE365@TQFP48 [DX3007]
W78LE51@PLCC44 [DX2044]
W78LE516 [DX0001]
W78LE516@TQFP44 [DX3002]
W78LE51C@PLCC44 [DX2044]
W78LE52 [DX0001]
W78LE52@TQFP44 [DX3002]
W78LE52C@PLCC44 [DX2044]
W78LE54 [DX0001]
W78LE54@TQFP44 [DX3002]
W78LE54C@PLCC44 [DX2044]
W78LE58 [DX0001]
W78LE58@TQFP44 [DX3002]
W78LE812@PLCC44 [DX2044]
W79E201@PLCC44 [DX2044]
W79E2051(dip14) [DX0001]
W79E2051(dip20) [DX0001]
W79E2051@SOIC16 [DX1033]
W79E2051R(dip20) [DX0001]
W79E216AFG@PQFP100 [DX3023]
W79E225ALG@TQFP48 [DX3007]
W79E226ALG@TQFP48 [DX3007]
W79E227ALG@TQFP48 [DX3007]
W79E4051(dip14) [DX0001]
W79E4051(dip20) [DX0001]
W79E4051@SOIC16 [DX1033]
W79E4051R(dip20) [DX0001]
W79E532 [DX0001]
W79E532@TQFP44 [DX3002]
W79E532A@PLCC44 [DX2044]
W79E533A@PLCC44 [DX2044]
W79E632@PLCC44 [DX2044]
W79E632A [DX0001]
W79E632A@TQFP44 [DX3002]
W79E648A@PLCC68 [DX2068]

W79E649A@PLCC68 [DX2068]
W79E658A@PQFP100 [DX3023]
W79E659A@QFP100 [DX3023]
W79E801A [DX0001]
W79E801A@SOIC20 [DX1033]
W79E802A [DX0001]
W79E802A@SOIC20 [DX1033]
W79E803A [DX0001]
W79E803A@SOIC20 [DX1033]
W79E804A [DX0001]
W79E804A@SOIC20 [DX1033]
W79E821A [DX0001]
W79E821A@SOIC20 [DX1033]
W79E822A [DX0001]
W79E822A@SOIC20 [DX1033]
W79E822B [DX0001]
W79E822B@SOIC20 [DX1033]
W79E823A [DX0001]
W79E823A@SOIC20 [DX1033]
W79E823B [DX0001]
W79E823B@SOIC20 [DX1033]
W79E824A [DX0001]
W79E824A@SOIC20 [DX1033]
W79E825A [DX0001]
W79E825A@SOIC20 [DX1033]
W79E831A [DX0001]
W79E831A@SOIC28 [DX1033]
W79E832A [DX0001]
W79E832A@SOIC28 [DX1033]
W79E833A [DX0001]
W79E833A@SOIC28 [DX1033]
W79E834A [DX0001]
W79E834A@SOIC28 [DX1033]
W79L532 [DX0001]
W79L532@PLCC44 [DX2044]
W79L532@TQFP44 [DX3002]
W79L549A@PLCC68 [DX2068]
W79L632 [DX0001]
W79L632@PLCC44 [DX2044]
W79L632@TQFP44 [DX3002]
W79L632A [DX0001]
W79L632A@PLCC44 [DX2044]
W79L632A@TQFP44 [DX3002]
W79L633A@PLCC44 [DX2044]
W79L648A@PLCC68 [DX2068]
W79L649A@PLCC68 [DX2068]
W79L658A@PQFP100 [DX3023]
W79L659A@QFP100 [DX3023]
W83960G@LQFP64 [DX3011]
W83L950D@TQFP80 [DX3016]
W83L950G@TQFP80 [DX3016]
W83L951ADG@LQFP128 [DX3030]
W83L951D@LQFP128 [DX3030]
W83L951DF@QFP128 [DX30UN]
W83L951DG@LQFP128 [DX3030]
W83L951F@QFP128 [DX30UN]
W925EP01@PQFP100 [DX3023]
W99100DG@TQFP48 [DX3007]

NXP

MICROCONTROLLER

61B0700 [DX1001]
61C0700 [DX1001]
61E0700 [DX1001]
EM773@QFN33 [DX4016]
LPC1110FD20 [DX1033]
LPC1110FDH20 [DX1027]
LPC1111/101@LQFP48 [DX3007]
LPC1111/101@QFN33 [DX4016]
LPC1111/101@QFP44 [DX3005]
LPC1111/102@LQFP48 [DX3007]
LPC1111/102@QFN33 [DX4016]
LPC1111/102@QFP44 [DX3005]
LPC1111/103@LQFP48 [DX3007]
LPC1111/103@QFN33 [DX4016]
LPC1111/103@QFP44 [DX3005]
LPC1111/201@LQFP48 [DX3007]
LPC1111/201@QFN33 [DX4016]
LPC1111/201@QFP44 [DX3005]
LPC1111/202@LQFP48 [DX3007]
LPC1111/202@QFN33 [DX4016]
LPC1111/202@QFP44 [DX3005]
LPC1111/203@LQFP48 [DX3007]
LPC1111/203@QFN33 [DX4016]
LPC1111/203@QFP44 [DX3005]
LPC1111@LQFP48 [DX3007]
LPC1111@QFN33 [DX4016]

LPC1111@QFP44 [DX3005]
LPC1111FD20 [DX1033]
LPC1111FDH20 [DX1033]
LPC1111FDH28 [DX1001]
LPC1111FHI33/303 [DX4015]
LPC1111FHN33/203@QFN32 [DX4016]
LPC1111FN28 [DX0001]
LPC1112/101@LQFP48 [DX3007]
LPC1112/101@QFN33 [DX4016]
LPC1112/101@QFP44 [DX3005]
LPC1112/102@LQFP48 [DX3007]
LPC1112/102@QFN33 [DX4016]
LPC1112/102@QFP44 [DX3005]
LPC1112/103@LQFP48 [DX3007]
LPC1112/103@QFN33 [DX4016]
LPC1112/103@QFP44 [DX3005]
LPC1112/201@LQFP48 [DX3007]
LPC1112/201@QFN33 [DX4016]
LPC1112/201@QFP44 [DX3005]
LPC1112/202@LQFP48 [DX3007]
LPC1112/202@QFN33 [DX4016]
LPC1112/202@QFP44 [DX3005]
LPC1112/203@LQFP48 [DX3007]
LPC1112/203@QFN33 [DX4016]
LPC1112/203@QFP44 [DX3005]
LPC1112@LQFP48 [DX3007]
LPC1112@QFN33 [DX4016]
LPC1112@QFP44 [DX3005]
LPC1112FD20 [DX1033]
LPC1112FDH20 [DX1033]
LPC1112FDH28 [DX1001]
LPC1112FHI33/303 [DX4015]
LPC1112FHN33/203 [DX4016]
LPC1112FN28 [DX0001]
LPC1113/101@LQFP48 [DX3007]
LPC1113/101@QFN33 [DX4016]
LPC1113/101@QFP44 [DX3005]
LPC1113/102@LQFP48 [DX3007]
LPC1113/102@QFN33 [DX4016]
LPC1113/102@QFP44 [DX3005]
LPC1113/103@LQFP48 [DX3007]
LPC1113/103@QFN33 [DX4016]
LPC1113/103@QFP44 [DX3005]
LPC1113/201@LQFP48 [DX3007]
LPC1113/201@QFN33 [DX4016]
LPC1113/201@QFP44 [DX3005]
LPC1113/202@LQFP48 [DX3007]
LPC1113/202@QFN33 [DX4016]
LPC1113/202@QFP44 [DX3005]
LPC1113/203@LQFP48 [DX3007]
LPC1113/203@QFN33 [DX4016]
LPC1113/203@QFP44 [DX3005]
LPC1113/301@QFN33 [DX4016]
LPC1113/301@QFP44 [DX3005]
LPC1113/301@QFP48 [DX3007]
LPC1113/302@QFN33 [DX4016]
LPC1113/302@QFP44 [DX3005]
LPC1113/302@QFP48 [DX3007]
LPC1113/303@QFN33 [DX4016]
LPC1113/303@QFP44 [DX3005]
LPC1113/303@QFP48 [DX3007]
LPC1113@LQFP48 [DX3007]
LPC1113@QFN33 [DX4016]
LPC1113@QFP44 [DX3005]
LPC1113FD20 [DX1033]
LPC1113FDH20 [DX1033]
LPC1113FDH28 [DX1001]
LPC1113FHI33/303 [DX4015]
LPC1113FHN33/203 [DX4016]
LPC1113FN28 [DX0001]
LPC1114/101@LQFP48 [DX3007]
LPC1114/101@QFN33 [DX4016]
LPC1114/101@QFP44 [DX3005]
LPC1114/102@LQFP48 [DX3007]
LPC1114/102@QFN33 [DX4016]
LPC1114/102@QFP44 [DX3005]
LPC1114/103@LQFP48 [DX3007]
LPC1114/103@QFN33 [DX4016]
LPC1114/103@QFP44 [DX3005]
LPC1114/201@LQFP48 [DX3007]
LPC1114/201@QFN33 [DX4016]
LPC1114/201@QFP44 [DX3005]
LPC1114/202@LQFP48 [DX3007]
LPC1114/202@QFN33 [DX4016]
LPC1114/202@QFP44 [DX3005]
LPC1114/203@LQFP48 [DX3007]
LPC1114/203@QFN33 [DX4016]
LPC1114/203@QFP44 [DX3005]
LPC1114/301@QFN33 [DX4016]
LPC1114/301@QFP44 [DX3005]
LPC1114/301@QFP48 [DX3007]
LPC1114/302@QFN33 [DX4016]
LPC1114/302@QFP44 [DX3005]
LPC1114/302@QFP48 [DX3007]
LPC1114/303@QFN33 [DX4016]
LPC1114/303@QFP44 [DX3005]

LPC1114/303@QFP48 [DX3007]
LPC1114/323@QFP44 [DX3005]
LPC1114/333@QFN33 [DX4016]
LPC1114/333@QFP48 [DX3007]
LPC1114@QFN33 [DX4016]
LPC1114FD20 [DX1033]
LPC1114FDH28 [DX1001]
LPC1114FHN33/203 [DX4016]
LPC1115/303@QFP48 [DX3007]
LPC11A11/001@QFP48 [DX3007]
LPC11A12/101@QFP48 [DX3007]
LPC11A13/201@QFP48 [DX3007]
LPC11A14/301@QFP48 [DX3007]
LPC11C12/102@LQFP48 [DX3007]
LPC11C12/201@LQFP48 [DX3007]
LPC11C12/203@LQFP48 [DX3007]
LPC11C12@LQFP48 [DX3007]
LPC11C14/102@LQFP48 [DX3007]
LPC11C14/201@LQFP48 [DX3007]
LPC11C14/203@LQFP48 [DX3007]
LPC11C14@LQFP48 [DX3007]
LPC11C22/102@LQFP48 [DX3007]
LPC11C22/201@LQFP48 [DX3007]
LPC11C22/203@LQFP48 [DX3007]
LPC11C22@LQFP48 [DX3007]
LPC11C24/102@LQFP48 [DX3007]
LPC11C24/201@LQFP48 [DX3007]
LPC11C24/203@LQFP48 [DX3007]
LPC11C24@LQFP48 [DX3007]
LPC11E11FHI33101 [DX4015]
LPC11E12@QFP48 [DX3007]
LPC11E13/301@QFP64 [DX3011]
LPC11E13@QFN33 [DX4016]
LPC11E13@QFP64 [DX3011]
LPC11E14/301@QFP64 [DX3011]
LPC11E14@QFN33 [DX4016]
LPC11E14@QFP64 [DX3011]
LPC11E23/301@QFN33 [DX4016]
LPC11E23/301@QFP64 [DX3011]
LPC11E23/401@QFN33 [DX4016]
LPC11E23/401@QFP64 [DX3011]
LPC11E23@QFN33 [DX4016]
LPC11E23@QFP64 [DX3011]
LPC11E24/301@QFN33 [DX4016]
LPC11E24/301@QFP64 [DX3011]
LPC11E24/401@QFN33 [DX4016]
LPC11E24/401@QFP64 [DX3011]
LPC11E24@QFN33 [DX4016]
LPC1114/323@QFN33 [DX4016]
LPC1114/323@QFP48 [DX3007]
LPC1114/333@QFP44 [DX3005]
LPC1114@LQFP48 [DX3007]
LPC1114@QFP44 [DX3005]
LPC1114FDH20 [DX1033]
LPC1114FHI33/303 [DX4015]
LPC1114FN28 [DX0001]
LPC11A11/001@QFN33 [DX4016]
LPC11A12/101@QFN33 [DX4016]
LPC11A13/201@QFN33 [DX4016]
LPC11A14/301@QFN33 [DX4016]
LPC11C12/101@LQFP48 [DX3007]
LPC11C12/103@LQFP48 [DX3007]
LPC11C12/202@LQFP48 [DX3007]
LPC11C12/301@LQFP48 [DX3007]
LPC11C14/101@LQFP48 [DX3007]
LPC11C14/103@LQFP48 [DX3007]
LPC11C14/202@LQFP48 [DX3007]
LPC11C14/301@LQFP48 [DX3007]
LPC11C22/101@LQFP48 [DX3007]
LPC11C22/103@LQFP48 [DX3007]
LPC11C22/202@LQFP48 [DX3007]
LPC11C22/301@LQFP48 [DX3007]
LPC11C24/101@LQFP48 [DX3007]
LPC11C24/103@LQFP48 [DX3007]
LPC11C24/202@LQFP48 [DX3007]
LPC11C24/301@LQFP48 [DX3007]
LPC11D14FBD100 [DX3043]
LPC11E12@QFN33 [DX4016]
LPC11E12@TFBGA48 [BBBB]
LPC11E13/401@QFP64 [DX3011]
LPC11E13@QFP48 [DX3007]
LPC11E13@TFBGA48 [BBBB]
LPC11E14/401@QFP64 [DX3011]
LPC11E14@QFP48 [DX3007]
LPC11E14@TFBGA48 [BBBB]
LPC11E23/301@QFP48 [DX3007]
LPC11E23/301@TFBGA48 [BBBB]
LPC11E23/401@QFP48 [DX3007]
LPC11E23/401@TFBGA48 [BBBB]
LPC11E23@QFP48 [DX3007]
LPC11E23@TFBGA48 [BBBB]
LPC11E24/301@QFP48 [DX3007]
LPC11E24/301@TFBGA48 [BBBB]
LPC11E24/401@QFP48 [DX3007]
LPC11E24/401@TFBGA48 [BBBB]
LPC11E24@QFP48 [DX3007]

LPC11E24@QFP64 [DX3011]
LPC11E24@TFBGA48 [BBBB]
LPC11U12@QFN33 [DX4016]
LPC11U12@QFP48 [DX3007]
LPC11U12@TFBGA48 [BBBB]
LPC11U13@QFN33 [DX4016]
LPC11U13@QFP48 [DX3007]
LPC11U13@TFBGA48 [BBBB]
LPC11U14@QFN33 [DX4016]
LPC11U14@QFP48 [DX3007]
LPC11U14@TFBGA48 [BBBB]
LPC11U23/301@QFN33 [DX4016]
LPC11U23/301@QFP48 [DX3007]
LPC11U23/301@QFP64 [DX3011]
LPC11U23/301@TFBGA48 [BBBB]
LPC11U23/401@QFN33 [DX4016]
LPC11U23/401@QFP48 [DX3007]
LPC11U23/401@QFP64 [DX3011]
LPC11U23/401@TFBGA48 [BBBB]
LPC11U23@QFN33 [DX4016]
LPC11U23@QFP48 [DX3007]
LPC11U23@QFP64 [DX3011]
LPC11U23@TFBGA48 [BBBB]
LPC11U24/301@QFN33 [DX4016]
LPC11U24/301@QFP48 [DX3007]
LPC11U24/301@QFP64 [DX3011]
LPC11U24/301@TFBGA48 [BBBB]
LPC11U24/401@QFN33 [DX4016]
LPC11U24/401@QFP48 [DX3007]
LPC11U24/401@QFP64 [DX3011]
LPC11U24/401@TFBGA48 [BBBB]
LPC11U24@QFN33 [DX4016]
LPC11U24@QFP48 [DX3007]
LPC11U24@QFP64 [DX3011]
LPC11U24@TFBGA48 [BBBB]
LPC11U33@QFN33 [DX4016]
LPC11U34/311@QFN33 [DX4016]
LPC11U34/421@QFN33 [DX4016]
LPC11U35/301@BGA48 [BBBB]
LPC11U35/301@QFP48 [DX3007]
LPC11U35/301@QFP64 [DX3011]
LPC11U35/401@BGA48 [BBBB]
LPC11U35/401@QFP48 [DX3007]
LPC11U35/401@QFP64 [DX3011]
LPC11U35/501@BGA48 [BBBB]
LPC11U35/501@QFP48 [DX3007]
LPC11U35/501@QFP64 [DX3011]
LPC11U35FHI33401 [DX4015]
LPC11U35FHI33501 [DX4015]
LPC11U36/301@BGA48 [BBBB]
LPC11U36/301@QFP48 [DX3007]
LPC11U36/301@QFP64 [DX3011]
LPC11U36/401@BGA48 [BBBB]
LPC11U36/401@QFP48 [DX3007]
LPC11U36/401@QFP64 [DX3011]
LPC11U36/501@BGA48 [BBBB]
LPC11U36/501@QFP48 [DX3007]
LPC11U36/501@QFP64 [DX3011]
LPC11U37/301@BGA48 [BBBB]
LPC11U37/301@QFP48 [DX3007]
LPC11U37/301@QFP64 [DX3011]
LPC11U37/401@BGA48 [BBBB]
LPC11U37/401@QFP48 [DX3007]
LPC11U37/401@QFP64 [DX3011]
LPC11U37/501@BGA48 [BBBB]
LPC11U37/501@QFP48 [DX3007]
LPC11U37/501@QFP64 [DX3011]
LPC1224/101@LQFP48 [DX3007]
LPC1224/101@LQFP64 [DX3011]
LPC1224/121@LQFP48 [DX3007]
LPC1224/121@LQFP64 [DX3011]
LPC1224/201@LQFP48 [DX3007]
LPC1224/201@LQFP64 [DX3011]
LPC1224/221@LQFP48 [DX3007]
LPC1224/221@LQFP64 [DX3011]
LPC1225/201@LQFP48 [DX3007]
LPC1225/201@LQFP64 [DX3011]
LPC1225/221@LQFP48 [DX3007]
LPC1225/221@LQFP64 [DX3011]
LPC1225/301@LQFP48 [DX3007]
LPC1225/301@LQFP64 [DX3011]
LPC1225/321@LQFP48 [DX3007]
LPC1225/321@LQFP64 [DX3011]
LPC1226/201@LQFP48 [DX3007]
LPC1226/201@LQFP64 [DX3011]
LPC1226/301@LQFP48 [DX3007]
LPC1226/301@LQFP64 [DX3011]
LPC1227/201@LQFP48 [DX3007]
LPC1227/201@LQFP64 [DX3011]
LPC1227/301@LQFP48 [DX3007]
LPC1227/301@LQFP64 [DX3011]
LPC12D27/201@LQFP100 [DX3043]
LPC12D27/201@LQFP48 [DX3007]
LPC12D27/201@LQFP64 [DX3011]
LPC12D27/301@LQFP100 [DX3043]
LPC12D27/301@LQFP48 [DX3007]

LPC12D27/301@LQFP64 [DX3011]
LPC1311@QFN33 [DX4016]
LPC1312@QFN33 [DX4016]
LPC1313@QFN33 [DX4016]
LPC1314@QFN33 [DX4016]
LPC1315FHN33 [DX4016]
LPC1316FHN33 [DX4016]
LPC1317FBD64 [DX3011]
LPC1341@LQFP48 [DX3007]
LPC1342@LQFP48 [DX3007]
LPC1343@LQFP48 [DX3007]
LPC1344@LQFP48 [DX3007]
LPC1345FBD48 [DX3007]
LPC1346FBD48 [DX3007]
LPC1347FBD48 [DX3007]
LPC1347FHN33 [DX4016]
LPC1752@LQFP80 [DX3016]
LPC1756@LQFP80 [DX3016]
LPC1759@LQFP80 [DX3016]
LPC1763FET100 [DX5055]
LPC1764FET100 [DX5055]
LPC1765FET100 [DX5055]
LPC1766FET100 [DX5055]
LPC1767FET100 [DX5055]
LPC1768FET100 [DX5055]
LPC1769FET100 [DX5055]
LPC1774FBD208 [DX3092]
LPC1774FET208 [BBBB]
LPC1775FBD208 [DX3092]
LPC1775FET208 [BBBB]
LPC1776FBD208 [DX3092]
LPC1776FET208 [BBBB]
LPC1777FBD208 [DX3092]
LPC1777FET208 [BBBB]
LPC1778FBD208 [DX3092]
LPC1778FET208 [BBBB]
LPC1784FBD208 [DX3092]
LPC1784FET208 [BBBB]
LPC1785FBD208 [DX3092]
LPC1785FET208 [BBBB]
LPC1786FBD208 [DX3092]
LPC1786FET208 [BBBB]
LPC1787FBD208 [DX3092]
LPC1787FET208 [BBBB]
LPC1788FBD208 [DX3092]
LPC1788FET208 [BBBB]
LPC2101FBD48/00@LQFP48 [DX3007]
LPC2101FBD48@LQFP48 [DX3007]
LPC1311@LQFP48 [DX3007]
LPC1312@LQFP48 [DX3007]
LPC1313@LQFP48 [DX3007]
LPC1314@LQFP48 [DX3007]
LPC1315FBD48 [DX3007]
LPC1316FBD48 [DX3007]
LPC1317FBD48 [DX3007]
LPC1317FHN33 [DX4016]
LPC1341@QFN33 [DX4016]
LPC1342@QFN33 [DX4016]
LPC1343@QFN33 [DX4016]
LPC1344@QFN33 [DX4016]
LPC1345FHN33 [DX4016]
LPC1346FHN33 [DX4016]
LPC1347FBD64 [DX3011]
LPC1751@LQFP80 [DX3016]
LPC1754@LQFP80 [DX3016]
LPC1758@LQFP80 [DX3016]
LPC1763@LQFP100 [DX3043]
LPC1764@LQFP100 [DX3043]
LPC1765@LQFP100 [DX3043]
LPC1766@LQFP100 [DX3043]
LPC1767@LQFP100 [DX3043]
LPC1768@LQFP100 [DX3043]
LPC1769@LQFP100 [DX3043]
LPC1774FBD144 [DX3051]
LPC1774FET180 [BBBB]
LPC1775FBD144 [DX3051]
LPC1775FET180 [BBBB]
LPC1776FBD144 [DX3051]
LPC1776FET180 [BBBB]
LPC1777FBD144 [DX3051]
LPC1777FET180 [BBBB]
LPC1778FBD144 [DX3051]
LPC1778FET180 [BBBB]
LPC1784FBD144 [DX3051]
LPC1784FET180 [BBBB]
LPC1785FBD144 [DX3051]
LPC1785FET180 [BBBB]
LPC1786FBD144 [DX3051]
LPC1786FET180 [BBBB]
LPC1787FBD144 [DX3051]
LPC1787FET180 [BBBB]
LPC1788FBD144 [DX3051]
LPC1788FET180 [BBBB]
LPC1827FBD144 [DX3051]
LPC2101FBD48/01@LQFP48 [DX3007]
LPC2101FHN48/00@HVQFN48 [DX4021]

LPC2101FHN48/01@HVQFN48 [DX4021]
LPC2101FHN48@HVQFN48 [DX4021]
LPC2102FBD48/00@LQFP48 [DX3007]
LPC2102FBD48/01@LQFP48 [DX3007]
LPC2102FBD48@LQFP48 [DX3007]
LPC2102FHN48/00@HVQFN48 [DX4021]
LPC2102FHN48/01@HVQFN48 [DX4021]
LPC2102FHN48@HVQFN48 [DX4021]
LPC2103FA44@PLCC44 [DX2144]
LPC2103FBD48/00@LQFP48 [DX3007]
LPC2103FBD48/01@LQFP48 [DX3007]
LPC2103FBD48@LQFP48 [DX3007]
LPC2103FHN48/00@HVQFN48 [DX4021]
LPC2103FHN48/01@HVQFN48 [DX4021]
LPC2103FHN48@HVQFN48 [DX4021]
LPC2104BBD48@LQFP48 [DX3007]
LPC2104FBD48/00@LQFP48 [DX3007]
LPC2104FBD48/01@LQFP48 [DX3007]
LPC2104FBD48@LQFP48 [DX3007]
LPC2104FHN48/00@HVQFN48 [DX4021]
LPC2104FHN48/01@HVQFN48 [DX4021]
LPC2104FHN48@HVQFN48 [DX4021]
LPC2105BBD48@LQFP48 [DX3007]
LPC2105FBD48/00@LQFP48 [DX3007]
LPC2105FBD48/01@LQFP48 [DX3007]
LPC2105FBD48@LQFP48 [DX3007]
LPC2105FHN48/00@HVQFN48 [DX4021]
LPC2105FHN48/01@HVQFN48 [DX4021]
LPC2105FHN48@HVQFN48 [DX4021]
LPC2106BBD48@LQFP48 [DX3007]
LPC2106FBD48/00@LQFP48 [DX3007]
LPC2106FBD48/01@LQFP48 [DX3007]
LPC2106FBD48@LQFP48 [DX3007]
LPC2106FHN48/00@HVQFN48 [DX4021]
LPC2106FHN48/01@HVQFN48 [DX4021]
LPC2106FHN48@HVQFN48 [DX4021]
LPC2109FBD64@LQFP64 [DX3011]
LPC2109FHN64@QFN64 [DX4023]
LPC2114FBD64@LQFP64 [DX3011]
LPC2114FHN64@QFN64 [DX4023]
LPC2119FBD64@LQFP64 [DX3011]
LPC2119FHN64@QFN64 [DX4023]
LPC2124FBD64@LQFP64 [DX3011]
LPC2124FHN64@QFN64 [DX4023]
LPC2129FBD64@LQFP64 [DX3011]
LPC2129FHN64@QFN64 [DX4023]
LPC2131FBD64@LQFP64 [DX3011]
LPC2131FBD64@LQFP64(new) [DX3057-8]
LPC2131FHN64@QFN64 [DX4023]
LPC2131FHN64@QFN64(new) [DX4023]
LPC2132FBD64@LQFP64 [DX3011]
LPC2132FBD64@LQFP64(new) [DX3057-8]
LPC2132FHN64@QFN64 [DX4023]
LPC2132FHN64@QFN64(new) [DX4023]
LPC2134FBD64@LQFP64 [DX3011]
LPC2134FBD64@LQFP64(new) [DX3057-8]
LPC2134FHN64@QFN64 [DX4023]
LPC2134FHN64@QFN64(new) [DX4023]
LPC2136FBD64@LQFP64 [DX3011]
LPC2136FBD64@LQFP64(new) [DX3057-8]
LPC2136FHN64@QFN64 [DX4023]
LPC2136FHN64@QFN64(new) [DX4023]
LPC2138FBD64@LQFP64 [DX3011]
LPC2138FBD64@LQFP64(new) [DX3057-8]
LPC2138FHN64@QFN64 [DX4023]
LPC2138FHN64@QFN64(new) [DX4023]
LPC2141FBD64@LQFP64 [DX3011]
LPC2142FBD64@LQFP64 [DX3011]
LPC2144FBD64@LQFP64 [DX3011]
LPC2146FBD64@LQFP64 [DX3011]
LPC2148FBD64@LQFP64 [DX3011]
LPC2194FBD64@LQFP64 [DX3011]
LPC2194FHN64@QFN64 [DX4023]
LPC2212HBD144@LQFP144 [DX3035]
LPC2214FBD144@LQFP144 [DX3035]
LPC2214HBD144@LQFP144 [DX3035]
LPC2292FBD144@LQFP144 [DX3035]
LPC2292HBD144@LQFP144 [DX3035]
LPC2294FBD144@LQFP144 [DX3035]
LPC2294HBD144@LQFP144 [DX3035]
LPC2361@LQFP100 [DX3021]
LPC2361@TFBGA100 [DX5055]
LPC2362@LQFP100 [DX3021]
LPC2362@TFBGA100 [DX5055]
LPC2364@LQFP100 [DX3021]
LPC2364@LQFP100(new) [DX3021]

LPC2364@TFBGA100 [DX5055]
LPC2364@TFBGA100(new) [DX5055]
LPC2365@LQFP100 [DX3021]
LPC2365@TFBGA100 [DX5055]
LPC2366@LQFP100 [DX3021]
LPC2366@LQFP100(new) [DX3021]
LPC2366@TFBGA100 [DX5055]
LPC2366@TFBGA100(new) [DX5055]
LPC2367@LQFP100 [DX3021]
LPC2367@TFBGA100 [DX5055]
LPC2368@LQFP100 [DX3021]
LPC2368@LQFP100(new) [DX3021]
LPC2368@TFBGA100 [DX5055]
LPC2368@TFBGA100(new) [DX5055]
LPC2377@LQFP144 [DX3035]
LPC2378(new)@LQFP144 [DX3035]
LPC2378@LQFP144 [DX3035]
LPC2387@LQFP100 [DX3021]
LPC2387@TFBGA100 [DX5055]
LPC2388@LQFP144 [DX3035]
LPC2458FET180 [DX5213]
LPC2458FET180N [DX5213]
LPC2468FBD208(new)@LQFP208(*) [DX3040]
LPC2468FBD208@LQFP208(*) [DX3040]
LPC2468FET208(new)@BGA208(*) [DX5125]
LPC2468FET208@BGA208(*) [DX5125]
LPC2478FBD208@LQFP208(*) [DX3040]
LPC2478FET208@BGA208(*) [DX5125]
LPC4072FBD144 [DX3051]
LPC4072FBD208 [DX3092]
LPC4072FBD80 [DX3016]
LPC4072FET180 [BBBB]
LPC4072FET208 [DX5253]
LPC4074FBD144 [DX3051]
LPC4074FBD208 [DX3092]
LPC4074FBD80 [DX3016]
LPC4074FET180 [BBBB]
LPC4074FET208 [DX5253]
LPC4076FBD144 [DX3051]
LPC4076FBD208 [DX3092]
LPC4076FBD80 [DX3016]
LPC4076FET180 [BBBB]
LPC4076FET208 [DX5253]
LPC4078FBD144 [DX3051]
LPC4078FBD208 [DX3092]
LPC4078FBD80 [DX3016]
LPC4078FET180 [BBBB]
LPC4078FET208 [DX5253]
LPC4088FBD144 [DX3051]
LPC4088FBD208 [DX3092]
LPC4088FBD80 [DX3016]
LPC4088FET180 [BBBB]
LPC4088FET208 [DX5253]
LPC810M021FN8 [DX1001]
LPC811M001FDH16 [DX1001]
LPC811M001JDH16 [DX1001]
LPC812M101FD20 [DX1033]
LPC812M101FDH16 [DX1001]
LPC812M101FDH20 [DX1001]
LPC812M101FTB16 [BBBB]
LPC812M101JD20 [DX1033]
LPC812M101JDH16 [DX1001]
LPC812M101JDH20 [DX1001]
LPC812M101JTB16 [BBBB]
LPC822M101JDH20 [DX1001]
LPC822M201JHI33 [DX4060]
LPC824M101JDH20 [DX1001]
LPC824M201JHI33 [DX4060]
OM4371FN [DX0001]
OM4371FN@PLCC44 [DX2044]
OM4371FN@TQFP44 [DX3005]
P83C660X2@PLCC44 [DX2044]
P83C660X2@TQFP44 [DX3005]
P83C661X2@PLCC44 [DX2044]
P83C661X2@TQFP44 [DX3005]
P87C054@SDIP42 [DX0042]
P87C055@SDIP42 [DX0042]
P87C451@PLCC68 [DX2068]
P87C451@SDIP64 [DX0064]
P87C453@PLCC68 [DX2068]
P87C51 [DX0001]
P87C51@PLCC44 [DX2044]
P87C51@TQFP44 [DX3002]
P87C51FA [DX0001]
P87C51FA@PLCC44 [DX2044]
P87C51FA@TQFP44 [DX3002]
P87C51FB [DX0001]
P87C51FB@PLCC44 [DX2044]
P87C51FB@TQFP44 [DX3002]
P87C51FC [DX0001]
P87C51FC@PLCC44 [DX2044]

P87C51FC@TQFP44 [DX3003]
P87C51MA2@PLCC44 [DX2044]
P87C51MB2@PLCC44 [DX2044]
P87C51MC2@PLCC44 [DX2044]
P87C51RA+ [DX0001]
P87C51RA+@PLCC44 [DX2044]
P87C51RA+@TQFP44 [DX3003]
P87C51RA2 [DX0001]
P87C51RA2@PLCC44 [DX2044]
P87C51RA2@TQFP44 [DX3002]
P87C51RB+ [DX0001]
P87C51RB+@PLCC44 [DX2044]
P87C51RB+@TQFP44 [DX3003]
P87C51RB2 [DX0001]
P87C51RB2@PLCC44 [DX2044]
P87C51RB2@TQFP44 [DX3002]
P87C51RC+ [DX0001]
P87C51RC+@PLCC44 [DX2044]
P87C51RC+@TQFP44 [DX3003]
P87C51RC2 [DX0001]
P87C51RC2@PLCC44 [DX2044]
P87C51RC2@TQFP44 [DX3002]
P87C51RD+ [DX0001]
P87C51RD+@PLCC44 [DX2044]
P87C51RD+@TQFP44 [DX3003]
P87C51RD2 [DX0001]
P87C51RD2@PLCC44 [DX2044]
P87C51RD2@TQFP44 [DX3003]
P87C51SB [DX0001]
P87C51SB@PLCC44 [DX2044]
P87C51SB@TQFP44 [DX3002]
P87C51SF [DX0001]
P87C51SF@PLCC44 [DX2044]
P87C51SF@TQFP44 [DX3002]
P87C51UB [DX0001]
P87C51UB@PLCC44 [DX2044]
P87C51UB@TQFP44 [DX3002]
P87C51UF [DX0001]
P87C51UF@PLCC44 [DX2044]
P87C51UF@TQFP44 [DX3002]
P87C51X2 [DX0001]
P87C51X2@PLCC44 [DX2044]
P87C51X2@TQFP44 [DX3005]
P87C51X2@TTSOP38 [DX1049]
P87C52 [DX0001]
P87C52@PLCC44 [DX2044]
P87C52@TQFP44 [DX3002]
P87C524 [DX0001]
P87C524@PLCC44 [DX2044]
P87C524@TQFP44 [DX3003]
P87C528 [DX0001]
P87C528@PLCC44 [DX2044]
P87C528@TQFP44 [DX3003]
P87C52SB [DX0001]
P87C52SB@PLCC44 [DX2044]
P87C52SB@TQFP44 [DX3002]
P87C52SF [DX0001]
P87C52SF@PLCC44 [DX2044]
P87C52SF@TQFP44 [DX3002]
P87C52UB [DX0001]
P87C52UB@PLCC44 [DX2044]
P87C52UB@TQFP44 [DX3002]
P87C52UF [DX0001]
P87C52UF@PLCC44 [DX2044]
P87C52UF@TQFP44 [DX3002]
P87C52X2 [DX0001]
P87C52X2@PLCC44 [DX2044]
P87C52X2@TQFP44 [DX3005]
P87C52X2@TTSOP38 [DX1049]
P87C54 [DX0001]
P87C54@PLCC44 [DX2044]
P87C54@TQFP44 [DX3002]
P87C54SB [DX0001]
P87C54SB@PLCC44 [DX2044]
P87C54SB@TQFP44 [DX3002]
P87C54SF [DX0001]
P87C54SF@PLCC44 [DX2044]
P87C54SF@TQFP44 [DX3002]
P87C54UB [DX0001]
P87C54UB@PLCC44 [DX2044]
P87C54UB@TQFP44 [DX3002]
P87C54UF [DX0001]
P87C54UF@PLCC44 [DX2044]
P87C54UF@TQFP44 [DX3002]
P87C54X2 [DX0001]
P87C54X2@PLCC44 [DX2044]
P87C54X2@TQFP44 [DX3005]
P87C54X2@TTSOP38 [DX1049]
P87C550 [DX0001]
P87C550@PLCC44 [DX2044]
P87C552@PLCC68 [DX2068]
P87C552@PQFP80 [DX3019]
P87C554@PLCC68 [DX2068]
P87C554@PQFP80 [DX3019]
P87C575 [DX0001]
P87C575@PLCC44 [DX2044]

P87C575@TQFP44 [DX3002]
P87C576 [DX0001]
P87C576@PLCC44 [DX2044]
P87C576@TQFP44 [DX3002]
P87C58 [DX0001]
P87C58@PLCC44 [DX2044]
P87C58@TQFP44 [DX3002]
P87C58SB [DX0001]
P87C58SB@PLCC44 [DX2044]
P87C58SB@TQFP44 [DX3002]
P87C58UB [DX0001]
P87C58UB@PLCC44 [DX2044]
P87C58UB@TQFP44 [DX3002]
P87C58X2 [DX0001]
P87C58X2@PLCC44 [DX2044]
P87C58X2@TQFP44 [DX3005]
P87C58X2@TTSOP38 [DX1049]
P87C591@PLCC44 [DX2044]
P87C591@TQFP44 [DX3002]
P87C592@PLCC68 [DX2068]
P87C652 [DX0001]
P87C652@PLCC44 [DX2044]
P87C652@TQFP44 [DX3002]
P87C654 [DX0001]
P87C654@PLCC44 [DX2044]
P87C654@TQFP44 [DX3002]
P87C660X2@PLCC44 [DX2044]
P87C660X2@TQFP44 [DX3005]
P87C661X2@PLCC44 [DX2044]
P87C661X2@TQFP44 [DX3005]
P87C748 [DX0001]
P87C748@PLCC28 [DX2028]
P87C749 [DX0001]
P87C749@PLCC28 [DX2028]
P87C750 [DX0001]
P87C750@PLCC28 [DX2028]
P87C750@SSOP24 [DX1026]
P87C751 [DX0001]
P87C751@PLCC28 [DX2028]
P87C751@SSOP24 [DX1026]
P87C752 [DX0001]
P87C752@PLCC28 [DX2028]
P87C752@SSOP28 [DX1026]
P87C754 [DX0001]
P87C754@PLCC28 [DX2028]
P87C754@SSOP28 [DX1026]
P87CL52X2 [DX0001]
P87CL52X2@PLCC44 [DX2044]
P87CL52X2@TQFP44 [DX3005]
P87CL52X2@TTSOP38 [DX1049]
P87CL54X2 [DX0001]
P87CL54X2@PLCC44 [DX2044]
P87CL54X2@TQFP44 [DX3005]
P87CL54X2@TTSOP38 [DX1049]
P87L51FA [DX0001]
P87L51FA@PLCC44 [DX2044]
P87L51FA@TQFP44 [DX3002]
P87L51FB [DX0001]
P87L51FB@PLCC44 [DX2044]
P87L51FB@TQFP44 [DX3002]
P87LPC759 [DX0001]
P87LPC759(ISP) [DX0001]
P87LPC760 [DX0001]
P87LPC760(ISP) [DX0001]
P87LPC760@TSSOP14 [DX1000]
P87LPC760@TSSOP14(ISP) [DX0001]
P87LPC761 [DX0001]
P87LPC761(ISP) [DX0001]
P87LPC762 [DX0001]
P87LPC762(ISP) [DX0001]
P87LPC762@PLCC44 [DX1044]
P87LPC762@PLCC44(ISP) [DX0001]
P87LPC762@SOIC20 [DX1033]
P87LPC762@SOIC20(ISP) [DX0001]
P87LPC764 [DX0001]
P87LPC764(ISP) [DX0001]
P87LPC764@PLCC44 [DX1044]
P87LPC764@PLCC44(ISP) [DX0001]
P87LPC764@SOIC20 [DX1033]
P87LPC764@SOIC20(ISP) [DX0001]
P87LPC764@TSSOP20 [DX1001]
P87LPC764@TSSOP20(ISP) [DX0001]
P87LPC767 [DX0001]
P87LPC767(ISP) [DX0001]
P87LPC767@PLCC44 [DX1044]
P87LPC767@PLCC44(ISP) [DX0001]
P87LPC767@SOIC20 [DX1033]
P87LPC767@SOIC20(ISP) [DX0001]
P87LPC768 [DX0001]
P87LPC768(ISP) [DX0001]
P87LPC768@SOIC20 [DX1033]
P87LPC768@SOIC20(ISP) [DX0001]
P87LPC769 [DX0001]
P87LPC769(ISP) [DX0001]
P87LPC769@PLCC44 [DX1044]
P87LPC769@PLCC44(ISP) [DX0001]

P87LPC769@SOIC20 [DX1033]
P87LPC769@SOIC20(ISP) [DX0001]
P87LPC778 [DX0001]
P87LPC778(ISP) [DX0001]
P87LPC778@TSSOP20 [DX1000]
P87LPC778@TSSOP20(ISP) [DX0001]
P87LPC779 [DX0001]
P87LPC779(ISP) [DX0001]
P87LPC779@TSSOP20 [DX1000]
P87LPC779@TSSOP20(ISP) [DX0001]
P89C138 [DX0001]
P89C138@PLCC44 [DX2044]
P89C138@TQFP44 [DX3005]
P89C238 [DX0001]
P89C238@PLCC44 [DX2044]
P89C238@TQFP44 [DX3005]
P89C51B [DX0001]
P89C51B@PLCC44 [DX2044]
P89C51B@TQFP44 [DX3005]
P89C51RA+ [DX0001]
P89C51RA+@PLCC44 [DX2044]
P89C51RA+@TQFP44 [DX3005]
P89C51RA2B [DX0001]
P89C51RA2B@PLCC44 [DX2044]
P89C51RA2B@TQFP44 [DX3005]
P89C51RB+ [DX0001]
P89C51RB+@PLCC44 [DX2044]
P89C51RB+@TQFP44 [DX3005]
P89C51RB2B [DX0001]
P89C51RB2B@PLCC44 [DX2044]
P89C51RB2B@TQFP44 [DX3005]
P89C51RB2H [DX0001]
P89C51RB2H@PLCC44 [DX2044]
P89C51RB2H@TQFP44 [DX3002]
P89C51RC+ [DX0001]
P89C51RC+@PLCC44 [DX2044]
P89C51RC+@TQFP44 [DX3005]
P89C51RC2B [DX0001]
P89C51RC2B@PLCC44 [DX2044]
P89C51RC2B@TQFP44 [DX3005]
P89C51RC2H [DX0001]
P89C51RC2H@PLCC44 [DX2044]
P89C51RC2H@TQFP44 [DX3002]
P89C51RD+ [DX0001]
P89C51RD+@PLCC44 [DX2044]
P89C51RD+@TQFP44 [DX3005]
P89C51RD2B [DX0001]
P89C51RD2B@PLCC44 [DX2044]
P89C51RD2B@TQFP44 [DX3005]
P89C51RD2H [DX0001]
P89C51RD2H@PLCC44 [DX2044]
P89C51RD2H@TQFP44 [DX3002]
P89C51UB [DX0001]
P89C51UB@PLCC44 [DX2044]
P89C51UB@TQFP44 [DX3005]
P89C51UF [DX0001]
P89C51UF@PLCC44 [DX2044]
P89C51UF@TQFP44 [DX3005]
P89C51X2 [DX0001]
P89C51X2@PLCC44 [DX2044]
P89C51X2@TQFP44 [DX3005]
P89C51X2B [DX0001]
P89C51X2B@PLCC44 [DX2044]
P89C51X2B@TQFP44 [DX3005]
P89C51X2F [DX0001]
P89C51X2F@PLCC44 [DX2044]
P89C51X2F@TQFP44 [DX3005]
P89C52 [DX0001]
P89C52@PLCC44 [DX2044]
P89C52@TQFP44 [DX3005]
P89C52B [DX0001]
P89C52B@PLCC44 [DX2044]
P89C52B@TQFP44 [DX3005]
P89C52UB [DX0001]
P89C52UB@PLCC44 [DX2044]
P89C52UB@TQFP44 [DX3005]
P89C52UF [DX0001]
P89C52UF@PLCC44 [DX2044]
P89C52UF@TQFP44 [DX3005]
P89C52X2 [DX0001]
P89C52X2@PLCC44 [DX2044]
P89C52X2@TQFP44 [DX3005]
P89C52X2B [DX0001]
P89C52X2B@PLCC44 [DX2044]
P89C52X2B@TQFP44 [DX3005]
P89C52X2F [DX0001]
P89C52X2F@PLCC44 [DX2044]
P89C52X2F@TQFP44 [DX3005]
P89C536@PLCC44 [DX2044]
P89C538@PLCC44 [DX2044]
P89C54 [DX0001]
P89C54@PLCC44 [DX2044]
P89C54@TQFP44 [DX3005]
P89C54B [DX0001]
P89C54B@PLCC44 [DX2044]
P89C54B@TQFP44 [DX3005]

P89C54UB [DX0001]
P89C54UB@PLCC44 [DX2044]
P89C54UB@TQFP44 [DX3005]
P89C54UF [DX0001]
P89C54UF@PLCC44 [DX2044]
P89C54UF@TQFP44 [DX3005]
P89C54X2 [DX0001]
P89C54X2@PLCC44 [DX2044]
P89C54X2@TQFP44 [DX3005]
P89C54X2B [DX0001]
P89C54X2B@PLCC44 [DX2044]
P89C54X2B@TQFP44 [DX3005]
P89C54X2F [DX0001]
P89C54X2F@PLCC44 [DX2044]
P89C54X2F@TQFP44 [DX3005]
P89C58 [DX0001]
P89C58@PLCC44 [DX2044]
P89C58@TQFP44 [DX3005]
P89C58B [DX0001]
P89C58B@PLCC44 [DX2044]
P89C58B@TQFP44 [DX3005]
P89C58UB [DX0001]
P89C58UB@PLCC44 [DX2044]
P89C58UB@TQFP44 [DX3005]
P89C58UF [DX0001]
P89C58UF@PLCC44 [DX2044]
P89C58UF@TQFP44 [DX3005]
P89C58X2 [DX0001]
P89C58X2@PLCC44 [DX2044]
P89C58X2@TQFP44 [DX3005]
P89C58X2B [DX0001]
P89C58X2B@PLCC44 [DX2044]
P89C58X2B@TQFP44 [DX3005]
P89C58X2F [DX0001]
P89C58X2F@PLCC44 [DX2044]
P89C58X2F@TQFP44 [DX3005]
P89C60X2 [DX0001]
P89C60X2@PLCC44 [DX2044]
P89C60X2@TQFP44 [DX3005]
P89C61X2 [DX0001]
P89C61X2@PLCC44 [DX2044]
P89C61X2@TQFP44 [DX3005]
P89C660 [DX0001]
P89C660@PLCC44 [DX2044]
P89C660@TQFP44 [DX3002]
P89C662 [DX0001]
P89C662@PLCC44 [DX2044]
P89C662@TQFP44 [DX3002]
P89C664 [DX0001]
P89C664@PLCC44 [DX2044]
P89C664@TQFP44 [DX3002]
P89C668 [DX0001]
P89C668@PLCC44 [DX2044]
P89C668@TQFP44 [DX3002]
P89C669 [DX0001]
P89C669@LQFP44 [DX3005]
P89C669@PLCC44 [DX2044]
P89C669X2 [DX0001]
P89C669X2@LQFP44 [DX3005]
P89C669X2@PLCC44 [DX2044]
P89C738 [DX0001]
P89C738@PLCC44 [DX2044]
P89C738@TQFP44 [DX3005]
P89C838 [DX0001]
P89C838@PLCC44 [DX2044]
P89C838@TQFP44 [DX3005]
P89CV51RB2@PLCC44 [DX2044]
P89CV51RB2@TQFP44 [DX3005]
P89CV51RC2@PLCC44 [DX2044]
P89CV51RC2@TQFP44 [DX3005]
P89CV51RD2@PLCC44 [DX2044]
P89CV51RD2@TQFP44 [DX3005]
P89LPC901(FD) [DX1045]
P89LPC901(FD)(ISP) [DX0001]
P89LPC901(FN) [DX0001]
P89LPC901(FN)(ISP) [DX0001]
P89LPC902(FD) [DX1045]
P89LPC902(FD)(ISP) [DX0001]
P89LPC902(FN) [DX0001]
P89LPC902(FN)(ISP) [DX0001]
P89LPC903(FD) [DX1045]
P89LPC903(FD)(ISP) [DX0001]
P89LPC904(FD) [DX1045]
P89LPC904(FD)(ISP) [DX0001]
P89LPC904(FN) [DX0001]
P89LPC904(FN)(ISP) [DX0001]
P89LPC906(FD) [DX1045]
P89LPC906(FD)(ISP) [DX0001]
P89LPC907(FD) [DX1045]
P89LPC907(FD)(ISP) [DX0001]
P89LPC908(FD) [DX1045]
P89LPC908(FD)(ISP) [DX0001]
P89LPC9102(FTK)@HVSON10 [DX4007]
P89LPC9103(FTK)@HVSON10 [DX4007]
P89LPC9107(FDH)@TSSOP14 [DX1001]
P89LPC9107(FN) [DX3001]

P89LPC912(FDH)@TSSOP14 [DX1000]
P89LPC912(FDH)@TSSOP14(ISP) [DX0001]
P89LPC913(FDH)@TSSOP14 [DX1000]
P89LPC913(FDH)@TSSOP14(ISP) [DX0001]
P89LPC914(FDH)@TSSOP14 [DX1000]
P89LPC914(FDH)@TSSOP14(ISP) [DX0001]
P89LPC915(FDH)@TSSOP14 [DX1000]
P89LPC915(FDH)@TSSOP14(ISP) [DX0001]
P89LPC916(FDH)@TSSOP16 [DX1000]
P89LPC916(FDH)@TSSOP16(ISP) [DX0001]
P89LPC917(FDH)@TSSOP16 [DX1000]
P89LPC917(FDH)@TSSOP16(ISP) [DX0001]
P89LPC920(FDH)@TSSOP20 [DX1000]
P89LPC920(FDH)@TSSOP20(ISP) [DX0001]
P89LPC920(FN) [DX0001]　　P89LPC920(FN)(ISP) [DX0001]
P89LPC9201(FDH)@TSSOP20 [DX1000]
P89LPC9201(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9201(FN) [DX0001]　　P89LPC9201(FN)(ISP) [DX0001]
P89LPC920A1(FDH)@TSSOP20 [DX1000]
P89LPC920A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC920A1(FN) [DX0001]　　P89LPC920A1(FN)(ISP) [DX0001]
P89LPC921(FDH)@TSSOP20 [DX1000]
P89LPC921(FDH)@TSSOP20(ISP) [DX0001]
P89LPC921(FN) [DX0001]　　P89LPC921(FN)(ISP) [DX0001]
P89LPC9211(FDH)@TSSOP20 [DX1000]
P89LPC9211(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9211(FN) [DX0001]　　P89LPC9211(FN)(ISP) [DX0001]
P89LPC921A1(FDH)@TSSOP20 [DX1000]
P89LPC921A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC921A1(FN) [DX0001]　　P89LPC921A1(FN)(ISP) [DX0001]
P89LPC922(FDH)@TSSOP20 [DX1000]
P89LPC922(FDH)@TSSOP20(ISP) [DX0001]
P89LPC922(FN) [DX0001]　　P89LPC922(FN)(ISP) [DX0001]
P89LPC9221(FDH)@TSSOP20 [DX1000]
P89LPC9221(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9221(FN) [DX0001]　　P89LPC9221(FN)(ISP) [DX0001]
P89LPC9221A1(FDH)@TSSOP20 [DX1000]
P89LPC9221A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9221A1(FN) [DX0001]　　P89LPC9221A1(FN)(ISP) [DX0001]
P89LPC922A1(FDH)@TSSOP20 [DX1000]
P89LPC922A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC922A1(FN) [DX0001]　　P89LPC922A1(FN)(ISP) [DX0001]
P89LPC924(FDH)@TSSOP20 [DX1000]
P89LPC924(FDH)@TSSOP20(ISP) [DX0001]
P89LPC924(FN) [DX0001]　　P89LPC924(FN)(ISP) [DX0001]
P89LPC9241(FDH)@TSSOP20 [DX1000]
P89LPC9241(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9241(FN) [DX0001]　　P89LPC9241(FN)(ISP) [DX0001]

P89LPC924A1(FDH)@TSSOP20 [DX1000]
P89LPC924A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC924A1(FN) [DX0001]
P89LPC924A1(FN)(ISP) [DX0001]
P89LPC925(FDH)@TSSOP20 [DX1000]
P89LPC925(FDH)@TSSOP20(ISP) [DX0001]
P89LPC925(FN) [DX0001]
P89LPC925(FN)(ISP) [DX0001]
P89LPC9251(FDH)@TSSOP20 [DX1000]
P89LPC9251(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9251(FN) [DX0001]
P89LPC9251(FN)(ISP) [DX0001]
P89LPC925A1(FDH)@TSSOP20 [DX1000]
P89LPC925A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC925A1(FN) [DX0001]
P89LPC925A1(FN)(ISP) [DX0001]
P89LPC930(BA)@PLCC28 [DX2028]
P89LPC930(BA)@PLCC28(ISP) [DX0001]
P89LPC930(BDH)@TSSOP28 [DX1001]
P89LPC930(BDH)@TSSOP28(ISP) [DX0001]
P89LPC9301(BA)@PLCC28 [DX2028]
P89LPC9301(BDH)@TSSOP28 [DX1001]
P89LPC9301FA [DX2028]
P89LPC9301FDH [DX1001]
P89LPC930FA [DX2028]
P89LPC930FDH [DX1001]
P89LPC931(BA)@PLCC28 [DX2028]
P89LPC931(BA)@PLCC28(ISP) [DX0001]
P89LPC931(BDH)@TSSOP28 [DX1001]
P89LPC931(BDH)@TSSOP28(ISP) [DX0001]
P89LPC9311(BA)@PLCC28 [DX2028]
P89LPC9311(BDH)@TSSOP28 [DX1001]
P89LPC9311FA [DX2028]
P89LPC9311FDH [DX1001]
P89LPC931FA [DX2028]
P89LPC931FDH [DX1001]
P89LPC932(BA)@PLCC28 [DX2028]
P89LPC932(BDH)@TSSOP28 [DX1001]
P89LPC932(FA)@PLCC28 [DX2028]
P89LPC93201BA@PLCC28 [DX2028]
P89LPC93201BDH@TSSOP28 [DX1001]
P89LPC93201FA@PLCC28 [DX2028]
P89LPC93201FDH@TSSOP28 [DX1001]
P89LPC93201FHN@QFN28 [DX4014]
P89LPC9321BA@PLCC28 [DX2028]
P89LPC9321BDH@TSSOP28 [DX1001]
P89LPC9321FA@PLCC28 [DX2028]
P89LPC9321FDH@TSSOP28 [DX1001]
P89LPC9321FHN@QFN28 [DX4014]
P89LPC932A1(BA)@PLCC28 [DX2028]
P89LPC932A1(BA)@PLCC28(ISP) [DX0001]
P89LPC932A1(BDH)@TSSOP28 [DX1001]
P89LPC932A1(BDH)@TSSOP28(ISP) [DX0001]
P89LPC932A1(FA)@PLCC28 [DX2028]
P89LPC932A1(FDH)@TSSOP28 [DX1001]
P89LPC932A1(FDH)@TSSOP28(ISP) [DX0001]
P89LPC932A1(FHN)@HVQFN28 [DX4014]
P89LPC932A1(FHN)@HVQFN28(ISP) [DX0001]
P89LPC933(BDH)@TSSOP28 [DX1001]
P89LPC933(BDH)@TSSOP28(ISP) [DX0001]
P89LPC933(FDH)@TSSOP28 [DX1001]
P89LPC933(FDH)@TSSOP28(ISP) [DX0001]
P89LPC933(HDH)@TSSOP28 [DX1001]
P89LPC9331(BDH)@TSSOP28 [DX1001]
P89LPC9331(FDH)@TSSOP28 [DX1001]
P89LPC9331(HDH)@TSSOP28 [DX1001]
P89LPC934(BDH)@TSSOP28 [DX1001]

P89LPC934(BDH)@TSSOP28(ISP) [DX0001]
P89LPC934(FDH)@TSSOP28 [DX1001]
P89LPC934(FDH)@TSSOP28(ISP) [DX0001]
P89LPC93401(FDH)@TSSOP28 [DX1001]
P89LPC93401V [DX0001]
P89LPC9341(BDH)@TSSOP28 [DX1001]
P89LPC9341(FDH)@TSSOP28 [DX1001]
P89LPC9341V [DX0001]
P89LPC935(BA)@PLCC28 [DX2028]
P89LPC935(BA)@PLCC28(ISP) [DX0001]
P89LPC935(BDH)@TSSOP28 [DX1001]
P89LPC935(BDH)@TSSOP28(ISP) [DX0001]
P89LPC935(FA)@PLCC28 [DX2028]
P89LPC935(FA)@PLCC28(ISP) [DX0001]
P89LPC935(FDH)@TSSOP28 [DX1001]
P89LPC935(FDH)@TSSOP28(ISP) [DX0001]
P89LPC935(FHN)@HVQFN28 [DX4014]
P89LPC935(FHN)@HVQFN28(ISP) [DX0001]
P89LPC93501BA@PLCC28 [DX2028]
P89LPC93501BDH@TSSOP28 [DX1001]
P89LPC93501FA@PLCC28 [DX2028]
P89LPC93501FDH@TSSOP28 [DX1001]
P89LPC93501FHN@QFN28 [DX4014]
P89LPC9351BA@PLCC28 [DX2028]
P89LPC9351BDH@TSSOP28 [DX1001]
P89LPC9351FA@PLCC28 [DX2028]
P89LPC9351FDH@TSSOP28 [DX1001]
P89LPC9351FHN@QFN28 [DX4014]
P89LPC936(FA)@PLCC28 [DX2028]
P89LPC936(FDH)@TSSOP28 [DX1001]
P89LPC9361(FA)@PLCC28 [DX2028]
P89LPC9361(FDH)@TSSOP28 [DX1001]
P89LPC938(FA)@PLCC28 [DX2028]
P89LPC938(FA)@PLCC28(ISP) [DX0001]
P89LPC938(FDH)@TSSOP28 [DX1001]
P89LPC938(FDH)@TSSOP28(ISP) [DX0001]
P89LPC938(FHN)@HVQFN28 [DX4014]
P89LPC938(FHN)@HVQFN28(ISP) [DX0001]
P89LPC93801BA@PLCC28 [DX2028]
P89LPC93801BDH@TSSOP28 [DX1001]
P89LPC93801FA@PLCC28 [DX2028]
P89LPC93801FDH@TSSOP28 [DX1001]
P89LPC93801FHN@QFN28 [DX4014]
P89LPC9381BA@PLCC28 [DX2028]
P89LPC9381BDH@TSSOP28 [DX1001]
P89LPC9381FA@PLCC28 [DX2028]
P89LPC9381FDH@TSSOP28 [DX1001]
P89LPC9381FHN@QFN28 [DX4014]
P89LPC9401(FBD)@LQFP64 [DX3013]
P89LPC9401(FBD)@LQFP64(ISP) [DX0001]
P89LPC9402(FBD)@LQFP64 [DX3013]
P89LPC9408(FBD)@LQFP64 [DX3013]
P89LPC9408(FBD)@LQFP64(ISP) [DX0001]
P89LPC952@LQFP44 [DX3005]
P89LPC952@LQFP44(ISP) [DX0001]
P89LPC952@LQFP48 [DX3007]
P89LPC952@LQFP48(ISP) [DX0001]
P89LPC952@PLCC44 [DX2044]
P89LPC952@PLCC44(ISP) [DX0001]
P89LPC954@LQFP44 [DX3005]
P89LPC954@LQFP44(ISP) [DX0001]
P89LPC954@LQFP48 [DX3007]
P89LPC954@LQFP48(ISP) [DX0001]
P89LPC954@PLCC44 [DX2044]
P89LPC954@PLCC44(ISP) [DX0001]
P89LPC970FDH@TSSOP20 [DX1000]
P89LPC970FDH@TSSOP20(serial) [DX1000]
P89LPC970FN [DX0001]
P89LPC970FN(serial) [DX0001]
P89LPC971FDH@TSSOP20 [DX1000]

P89LPC971FDH@TSSOP20(serial) [DX1000]
P89LPC971FN [DX0001]
P89LPC971FN(serial) [DX0001]
P89LPC972FDH@TSSOP20 [DX1000]
P89LPC972FDH@TSSOP20(serial) [DX1000]
P89LPC972FN [DX0001]
P89LPC972FN(serial) [DX0001]
P89LPC980FDH@TSSOP28 [DX1001]
P89LPC980FDH@TSSOP28(serial) [DX1001]
P89LPC982FDH@TSSOP28 [DX1001]
P89LPC982FDH@TSSOP28(serial) [DX1001]
P89LPC983FA@PLCC28 [DX2028]
P89LPC983FA@PLCC28(serial) [DX2028]
P89LPC983FDH@TSSOP28 [DX1001]
P89LPC983FDH@TSSOP28(serial) [DX1001]
P89LPC985FA@PLCC28 [DX2028]
P89LPC985FA@PLCC28(serial) [DX2028]
P89LPC985FDH@TSSOP28 [DX1001]
P89LPC985FDH@TSSOP28(serial) [DX1001]
P89LPC9902FTK [DX4047]
P89LPC9903FTK [DX4047]
P89LV51RB2 [DX0001]
P89LV51RB2@PLCC44 [DX2044]
P89LV51RB2@TQFP44 [DX3005]
P89LV51RB2FA@PLCC44 [DX2044]
P89LV51RB2FBC@TQFP44 [DX3005]
P89LV51RB2FN [DX0001]
P89LV51RC2 [DX0001]
P89LV51RC2@PLCC44 [DX2044]
P89LV51RC2@TQFP44 [DX3005]
P89LV51RC2FA@PLCC44 [DX2044]
P89LV51RC2FBC@TQFP44 [DX3005]
P89LV51RC2FN [DX0001]
P89LV51RD2 [DX0001]
P89LV51RD2(new) [DX0001]
P89LV51RD2(new)@PLCC44 [DX2044]
P89LV51RD2(new)@TQFP44 [DX3005]
P89LV51RD2@PLCC44 [DX2044]
P89LV51RD2@TQFP44 [DX3005]
P89LV51RD2BA(new)@PLCC44 [DX2044]
P89LV51RD2BA@PLCC44 [DX2044]
P89LV51RD2BBC(new)@TQFP44 [DX3005]
P89LV51RD2BBC@TQFP44 [DX3005]
P89LV51RD2BN [DX0001]
P89LV51RD2BN(new) [DX0001]
P89LV51RD2FA(new)@PLCC44 [DX2044]
P89LV51RD2FA@PLCC44 [DX2044]
P89LV51RD2FBC(new)@TQFP44 [DX3005]
P89LV51RD2FBC@TQFP44 [DX3005]
P89LV51RD2FN [DX0001]
P89LV51RD2FN(new) [DX0001]
P89V51RB2 [DX0001]
P89V51RB2@PLCC44 [DX2044]
P89V51RB2@TQFP44 [DX3005]
P89V51RB2FA@PLCC44 [DX2044]
P89V51RB2FBC@TQFP44 [DX3005]
P89V51RB2FN [DX0001]
P89V51RC2 [DX0001]
P89V51RC2@PLCC44 [DX2044]
P89V51RC2@TQFP44 [DX3005]
P89V51RC2FA@PLCC44 [DX2044]
P89V51RC2FBC@TQFP44 [DX3005]
P89V51RC2FN [DX0001]
P89V51RD2 [DX0001]
P89V51RD2(new) [DX0001]
P89V51RD2(new)@PLCC44 [DX2044]
P89V51RD2(new)@TQFP44 [DX3005]
P89V51RD2@PLCC44 [DX2044]
P89V51RD2@TQFP44 [DX3005]
P89V51RD2BA(new)@PLCC44 [DX2044]
P89V51RD2BA@PLCC44 [DX2044]
P89V51RD2BBC(new)@TQFP44 [DX3005]

P89V51RD2BBC@TQFP44 [DX3005]
P89V51RD2BN [DX0001]
P89V51RD2BN(new) [DX0001]
P89V51RD2FA(new)@PLCC44 [DX2044]
P89V51RD2FA@PLCC44 [DX2044]
P89V51RD2FBC(new)@TQFP44 [DX3005]
P89V51RD2FBC@TQFP44 [DX3005]
P89V51RD2FN [DX0001]
P89V51RD2FN(new) [DX0001]
P89V52X2 [DX0001]
P89V52X2(ISP) [DX0001]
P89V52X2@PLCC44 [DX2044]
P89V52X2@PLCC44(ISP) [DX0001]
P89V52X2@TQFP44 [DX3005]
P89V52X2@TQFP44(ISP) [DX0001]
P89V54X2 [DX0001]
P89V54X2(ISP) [DX0001]
P89V54X2@PLCC44 [DX2044]
P89V54X2@PLCC44(ISP) [DX0001]
P89V54X2@TQFP44 [DX3005]
P89V54X2@TQFP44(ISP) [DX0001]
P89V660@PLCC44 [DX2044]
P89V660@TQFP44 [DX3005]
P89V662@PLCC44 [DX2044]
P89V662@TQFP44 [DX3005]
P89V664@PLCC44 [DX2044]
P89V664@TQFP44 [DX3005]
PCF7931 [DX1026]
PCF7931ATS [DX1026]
PCF7931ATSM1AB [DX1026]
PCF7931ATSM2AB [DX1026]
PCF7931ATT [DX1001]
PCF7931ATTM1AB [DX1001]
PCF7931ATTM2AB [DX1001]
PCF7931M1AB [DX1026]
PCF7931M2AB [DX1026]
PCF7941 [DX1026]
PCF7941ATS [DX1026]
PCF7941ATSM1AB [DX1026]
PCF7941ATSM2AB [DX1026]
PCF7941ATT [DX1001]
PCF7941ATTM1AB [DX1001]
PCF7941ATTM2AB [DX1001]
PCF7941M1AB [DX1026]
PCF7941M2AB [DX1026]
PCF7945 [DX1001]
PCF7952AC1500 [DX1000]
PCF7952ATT [DX1000]
PCF7953AC1500@TSSOP28 [DX1001]
PCF7961ATTM1AB [DX1001]
PCF7961ATTM1AC [DX1001]
PCF7961ATTM1AE [DX1001]
PCH7971 [DX1081]
PXAC37@PLCC44 [DX2044]
PXAC37@TQFP44 [DX3003]
PXAG17@PLCC44 [DX2044]
PXAG17@TQFP44 [DX3003]
PXAG27@PLCC44 [DX2044]
PXAG27@TQFP44 [DX3003]
PXAG37@PLCC44 [DX2044]
PXAG37@TQFP44 [DX3003]
PXAG39@PLCC44 [DX2044]
PXAG39@TQFP44 [DX3003]
PXAG39K@PLCC44 [DX2044]
PXAG39K@TQFP44 [DX3003]
PXAG49@PLCC44 [DX2044]
PXAG49@TQFP44 [DX3003]
PXAG49K@PLCC44 [DX2044]
PXAG49K@TQFP44 [DX3003]
PXAS37@PLCC68 [DX2068]
PXAS37@PQFP80 [DX3016]
SE97B@QFN8 [DX4002]
SP30 [DX1081]
SP37 [DX1081]
SP370 [DX1081]
SP373 [DX1081]
TDA11105H@PQFP80 [DX3019]
TDA11105H1@PQFP80 [DX3019]
TDA11105PS@SDIP64 [DX0064]
TDA11106H@PQFP80 [DX3019]
TDA11106H1@PQFP80 [DX3019]
TDA11106PS@SDIP64 [DX0064]
TDA11112H@PQFP80 [DX3019]
TDA11112H1@PQFP80 [DX3019]
TDA11112PS@SDIP64 [DX0064]
TDA11115H@PQFP80 [DX3019]
TDA11115H1@PQFP80 [DX3019]
TDA11115PS@SDIP64 [DX0064]
TDA11116H@PQFP80 [DX3019]
TDA11116H1@PQFP80 [DX3019]
TDA11116PS@SDIP64 [DX0064]
TDA11125H@PQFP80 [DX3019]
TDA11125H1@PQFP80 [DX3019]
TDA11125PS@SDIP64 [DX0064]

TDA11126H@PQFP80 [DX3019]
TDA11126H1@PQFP80 [DX3019]
TDA11126PS@SDIP64 [DX0064]
TDA11135H@PQFP80 [DX3019]
TDA11135H1@PQFP80 [DX3019]
TDA11135PS@SDIP64 [DX0064]
TDA11136H@PQFP80 [DX3019]
TDA11136H1@PQFP80 [DX3019]
TDA11136PS@SDIP64 [DX0064]
TDA11142H@PQFP80 [DX3019]
TDA11142H1@PQFP80 [DX3019]
TDA11142PS@SDIP64 [DX0064]
TDA11145H@PQFP80 [DX3019]
TDA11145H1@PQFP80 [DX3019]
TDA11145PS@SDIP64 [DX0064]
TDA11146H@PQFP80 [DX3019]
TDA11146H1@PQFP80 [DX3019]
TDA11146PS@SDIP64 [DX0064]
TDA11155H@PQFP80 [DX3019]
TDA11155H1@PQFP80 [DX3019]
TDA11155PS@SDIP64 [DX0064]
TDA11156H@PQFP80 [DX3019]
TDA11156H1@PQFP80 [DX3019]
TDA11156PS@SDIP64 [DX0064]
TDA12100H@PQFP80 [DX3019]
TDA12100H1@PQFP80 [DX3019]
TDA12110H@PQFP80 [DX3019]
TDA12110H1@PQFP80 [DX3019]
TDA12120H@PQFP80 [DX3019]
TDA12120H1@PQFP80 [DX3019]
TDA12135H@PQFP80 [DX3019]
TDA12135H1@PQFP80 [DX3019]
TDA12135PS@SDIP64 [DX0064]
TDA12136H@PQFP80 [DX3019]
TDA12136H1@PQFP80 [DX3019]
TDA12136PS@SDIP64 [DX0064]
TDA12140H@PQFP80 [DX3019]
TDA12140H1@PQFP80 [DX3019]
TDA12155H@PQFP80 [DX3019]
TDA12155H1@PQFP80 [DX3019]
TDA12155PS@SDIP64 [DX0064]
TDA12156H@PQFP80 [DX3019]
TDA12156H1@PQFP80 [DX3019]
TDA12156PS@SDIP64 [DX0064]
TDA12165H@PQFP80 [DX3019]
TDA12165H1@PQFP80 [DX3019]
TDA12165PS@SDIP64 [DX0064]
TDA12166H@PQFP80 [DX3019]
TDA12166H1@PQFP80 [DX3019]
TDA12166PS@SDIP64 [DX0064]
TDA12175H@PQFP80 [DX3019]
TDA12175H1@PQFP80 [DX3019]
TDA12175PS@SDIP64 [DX0064]
TDA12176H@PQFP80 [DX3019]
TDA12176H1@PQFP80 [DX3019]
TDA12176PS@SDIP64 [DX0064]
TDA12185H@PQFP80 [DX3019]
TDA12185H1@PQFP80 [DX3019]
TDA12185PS@SDIP64 [DX0064]
TDA12186H@PQFP80 [DX3019]
TDA12186H1@PQFP80 [DX3019]
TDA12186PS@SDIP64 [DX0064]
TDA12195H@PQFP80 [DX3019]
TDA12195H1@PQFP80 [DX3019]
TDA12195PS@SDIP64 [DX0064]
TDA12196H@PQFP80 [DX3019]
TDA12196H1@PQFP80 [DX3019]
TDA12196PS@SDIP64 [DX0064]
UOCIIIN1A-128K@QIP90 [DX0090]
UOCIIIN1A-128K@QIP90(facedown) [DX0090]
UOCIIIN1A-128K@TQFP128 [DX3033]
UOCIIIN1A-128K@TQFP128(facedown) [DX3033]
UOCIIIN1A-256K@QIP90 [DX0090]
UOCIIIN1A-256K@QIP90(facedown) [DX0090]
UOCIIIN1A-256K@TQFP128 [DX3033]
UOCIIIN1A-256K@TQFP128(facedown) [DX3033]
UOCIIIN1B-128K@QIP90 [DX0090]
UOCIIIN1B-128K@QIP90(facedown) [DX0090]
UOCIIIN1B-128K@TQFP128 [DX3033]
UOCIIIN1B-128K@TQFP128(facedown) [DX3033]
UOCIIIN1B-256K@QIP90 [DX0090]
UOCIIIN1B-256K@QIP90(facedown) [DX0090]

UOCIIIN1B-256K@TQFP128 [DX3033]
UOCIIIN1B-256K@TQFP128(facedown) [DX3033]
UOCIIIN1D-128K@QIP90 [DX0090]
UOCIIIN1D-128K@QIP90(facedown) [DX0090]
UOCIIIN1D-128K@TQFP128 [DX3033]
UOCIIIN1D-128K@TQFP128(facedown) [DX3033]
UOCIIIN1D-256K@QIP90 [DX0090]
UOCIIIN1D-256K@QIP90(facedown) [DX0090]
UOCIIIN1D-256K@TQFP128 [DX3033]
UOCIIIN1D-256K@TQFP128(facedown) [DX3033]
UOCIIIN1E-128K@QIP90 [DX0090]
UOCIIIN1E-128K@QIP90(facedown) [DX0090]
UOCIIIN1E-128K@TQFP128 [DX3033]
UOCIIIN1E-128K@TQFP128(facedown) [DX3033]
UOCIIIN1E-256K@QIP90 [DX0090]
UOCIIIN1E-256K@QIP90(facedown) [DX0090]
UOCIIIN1E-256K@TQFP128 [DX3033]
UOCIIIN1E-256K@TQFP128(facedown) [DX3033]
UOCIIIN1F-128K@QIP90 [DX0090]
UOCIIIN1F-128K@QIP90(facedown) [DX0090]
UOCIIIN1F-128K@TQFP128 [DX3033]
UOCIIIN1F-128K@TQFP128(facedown) [DX3033]
UOCIIIN1F-256K@QIP90 [DX0090]
UOCIIIN1F-256K@QIP90(facedown) [DX0090]
UOCIIIN1F-256K@TQFP128 [DX3033]
UOCIIIN1F-256K@TQFP128(facedown) [DX3033]

OKI

E(E)PROM/FRAM/NVRAM

MR27V1652E@PSOP44 [DX1014]
MR27V401D@PSOP32 [DX1014]
MR27V401E [DX0001]
MR27V401E@TSOP32 [DX1003]
MR27V402D@PSOP40 [DX1022]
MR27V402E [DX0001]
MR27V402E@TSOP44 [DX1014]
MR27V802F@TSOP44 [DX1010]
MSM16812(08bit) [DX0001]
MSM271000 [DX0001]
MSM271000@TSOP32 [DX1002]
MSM271000AS@PLCC32 [DX2032]
MSM27128 [DX0001]
MSM27128AS [DX0001]
MSM2716 [DX0001]
MSM27256AS [DX0001]
MR27V401D [DX0001]
MR27V401D@TSOP32 [DX1003]
MR27V401E@PSOP32 [DX1014]
MR27V402D [DX0001]
MR27V402D@TSOP44 [DX1014]
MR27V402E@PSOP40 [DX1022]
MR27V802F@PSOP44 [DX1014]
MR27V802F@TSOP48 [DX1004]
MSM16812(08bit)@SOIC8 [DX1045]
MSM271000@PLCC32 [DX2032]
MSM271000AS [DX0001]
MSM271000AS@TSOP32 [DX1002]
MSM27128A [DX0001]
MSM27128AZB-RS [DX0001]
MSM27256 [DX0001]
MSM27256ZB-RS [DX0001]

MSM2732 [DX0001]
MSM2732A [DX0001]
MSM27512 [DX0001]
MSM27512AS [DX0001]
MSM27512ZB-RS [DX0001]
MSM2764 [DX0001]
MSM2764A [DX0001]
MSM2764AS [DX0001]
MSM2764AZB-RS [DX0001]
MSM2764RS [DX0001]
MSM27C1024 [DX0001]
MSM27C1024AS [DX0001]
MSM27C128 [DX0001]
MSM27C128AZB-RS [DX0001]
MSM27C256 [DX0001]
MSM27C256A [DX0001]
MSM27C256H [DX0001]
MSM27C256HZB [DX0001]
MSM27C256ZB [DX0001]
MSM27C64AS [DX0001]
MSM27C802CZ [DX0001]
MSM27C802CZ@PSOP44 [DX1014]
MSM27C802CZ@TSOP44 [DX1011]
MSM2816A(RS) [DX0001]
MSM28C16A [DX0001]

DRAM & SRAM

MSM51256 [DX0001]
MSM51256@SOIC28 [DX1035]
MSM51257AL [DX0001]
MSM51257AL@SOIC28 [DX1035]
MSM51257ALL [DX0001]
MSM51257ALL@SOIC28 [DX1035]
MSM5165AL [DX0001]
MSM5165AL@SOIC28 [DX1035]

ON

E(E)PROM/FRAM/NVRAM

CAT24C512 [DX0001]
CAT24C512@MSOP8 [DX1015]
CAT24C512@SOIC8[150 mil] [DX1045]
CAT24C512@SOIC8[200 mil] [DX1044]
CAT24C512@TSSOP8 [DX1059]
CTA24C512@UDFN8 [DX4006]

ON Semiconductor

E(E)PROM/FRAM/NVRAM

CAT13001(08bit)@SOIC8 [DX1045]
CAT13001(16bit)@SOIC8 [DX1045]
CAT13004(08bit)@SOIC8 [DX1045]
CAT13004(16bit)@SOIC8 [DX1045]
CAT13008(08bit)@SOIC8 [DX1045]
CAT13008(16bit)@SOIC8 [DX1045]
CAT13016(08bit)@SOIC8 [DX1045]
CAT13016(16bit)@SOIC8 [DX1045]
CAT1320 [DX0001]
CAT1320@SOIC8 [DX1045]
CAT1320@TDFN8 [DX0001]
CAT1320@TSSOP8 [DX1059]
CAT1321 [DX0001]
CAT1321@SOIC8 [DX1045]
CAT1321@TDFN8 [DX0001]
CAT1321@TSSOP8 [DX1059]
CAT14002@SOIC8 [DX1045]
CAT14004@SOIC8 [DX1045]
CAT14008@SOIC8 [DX1045]
CAT14016@SOIC8 [DX1045]
CAT15002@SOIC8 [DX1045]
CAT15004@SOIC8 [DX1045]
CAT15008@SOIC8 [DX1045]
CAT15016@SOIC8 [DX1045]

CAT1640 [DX0001]
CAT1640@SOIC8 [DX1045]
CAT1640@TDFN8 [DX0001]
CAT1640@TSSOP8 [DX1059]
CAT1641 [DX0001]
CAT1641@SOIC8 [DX1045]
CAT1641@TDFN8 [DX0001]
CAT1641@TSSOP8 [DX1059]
CAT24AA01@SOIC8 [DX1045]
CAT24AA01@TSOT-23 [DX1041]
CAT24AA02@SOIC8 [DX1045]
CAT24AA02@TSOT-23 [DX1041]
CAT24AA04@SOIC8 [DX1045]
CAT24AA04@TSOT-23 [DX1041]
CAT24AA08@SOIC8 [DX1045]
CAT24AA08@TSOT-23 [DX1041]
CAT24AA16@SOIC8 [DX1045]
CAT24AA16@TSOT-23 [DX1041]
CAT24C32 [DX0001]
CAT24C32@SOIC8 [DX1045]
CAT24C32@TDFN8 [DX4047]
CAT24C32@TSSOP8 [DX1059]
CAT24C32@UDFN8 [DX4047]
CAT34TS02@TDFN8 [DX0001]
CAT93C46R(08bit) [DX0001]
CAT93C46R(08bit)(V)@SOIC8 [DX1045]
CAT93C46R(08bit)(VP2)@TDFN8 [DX4002]
CAT93C46R(08bit)(W)@SOIC8 [DX1045]
CAT93C46R(08bit)(X)@SOIC8 [DX1045]
CAT93C46R(08bit)(Y)@TSSOP8 [DX1059]
CAT93C46R(16bit)(V)@SOIC8 [DX1045]
CAT93C46R(16bit)(VP2)@TDFN8 [DX4002]
CAT93C46R(16bit)(W)@SOIC8 [DX1045]
CAT93C46R(16bit)(X)@SOIC8 [DX1045]
CAT93C46R(16bit)(Y)@TSSOP8 [DX1059]
CAT93C46R-16 [DX0001]
CAT93C56(08bit) [DX0001]
CAT93C56(08bit)@SOIC8(150mil) [DX1045]
CAT93C56(08bit)@SOIC8(208mil) [DX1044]
CAT93C56(08bit)@TSSOP8 [DX1059]
CAT93C56(08bit)TDFN8(2*3) [DX4002]
CAT93C56(08bit)TDFN8(3*3) [DX4003]
CAT93C56(16bit) [DX0001]
CAT93C56(16bit)@SOIC8(150mil) [DX1045]
CAT93C56(16bit)@SOIC8(208mil) [DX1044]
CAT93C56(16bit)@TSSOP8 [DX1059]
CAT93C56(16bit)TDFN8(2*3) [DX4002]
CAT93C56(16bit)TDFN8(3*3) [DX4003]
CAT93C57(08bit) [DX0001]
CAT93C57(08bit)@SOIC8(150mil) [DX1045]
CAT93C57(08bit)@SOIC8(208mil) [DX1044]
CAT93C57(08bit)@TSSOP8 [DX1059]
CAT93C57(08bit)TDFN8(2*3) [DX4002]
CAT93C57(08bit)TDFN8(3*3) [DX4003]
CAT93C57(16bit) [DX0001]
CAT93C57(16bit)@SOIC8(150mil) [DX1045]
CAT93C57(16bit)@SOIC8(208mil) [DX1044]
CAT93C57(16bit)@TSSOP8 [DX1059]
CAT93C57(16bit)TDFN8(2*3) [DX4002]
CAT93C57(16bit)TDFN8(3*3) [DX4003]
CAV24C02@SOIC8 [DX1045]
CAV24C02@TSSOP8 [DX1059]

CAV24C04@SOIC8 [DX1045]
CAV24C08@SOIC8 [DX1045]
CAV24C16@SOIC8 [DX1045]
CAV24C32@SOIC8 [DX1045]
CAV24C64@SOIC8 [DX1045]
CAV24C04@TSSOP8 [DX1059]
CAV24C08@TSSOP8 [DX1059]
CAV24C16@TSSOP8 [DX1059]
CAV24C32@TSSOP8 [DX1059]
CAV24C64@TSSOP8 [DX1059]

MICROCONTROLLER

LC87F2C64A@QFP80 [DX3018]
LC87F2G08A [DX1012]
LC87F2J04A@SQFP48 [DX3007]
LC87F2J08A@SQFP48 [DX3007]
LC87F2J16A@SQFP48 [DX3007]
LC87F2J32A@SQFP48 [DX3007]
LC87F5G32A@SQFP48 [DX3007]
LC87F5VP6AU@QIP100E [DX3022]
LC87F2C64A@TQFP80 [DX3016]
LC87F2J04A@QIP48E [DX3093]
LC87F2J08A@QIP48E [DX3093]
LC87F2J16A@QIP48E [DX3093]
LC87F2J32A@QIP48E [DX3093]
LC87F5G32A@QIP48E [DX3093]
LC87F5N62B@QIP100E [DX3022]

On-Bright

MICROCONTROLLER

OB37R04A1@SOP10 [DX1016]
OB37R04A1@SOP16 [DX1016]
OB37R259A@SOP16 [DX1016]
OB39A08T1@SOP16 [DX1016]
OB39A08T1@SOP24 [DX1033]
OB39A08T2@SOP24 [DX1033]
OB39A16D1@QFP48 [DX3007]
OB39A16T1@QFP32 [DX3001]
OB39A16T1@SOP20 [DX1033]
OB39A16T1@SOP28 [DX1033]
OB37R04A1@SOP14 [DX1016]
OB37R259A@SOP14 [DX1016]
OB39A08T1@QFP32 [DX3001]
OB39A08T1@SOP20 [DX1033]
OB39A08T1@SOP28 [DX1033]
OB39A08T2@SOP28 [DX1033]
OB39A16D2@QFP48 [DX3007]
OB39A16T1@SOP16 [DX1016]
OB39A16T1@SOP24 [DX1033]

PANASONIC

MICROCONTROLLER

MN101EF31G [DX3017]
MN101EF32D@QFP64(parallel) [DX3013]
MN101EF56K [BBBB]
MN101EF76K [BBBB]
MN103SFC2D [DX3003]
MN103SFE4K [DX3017]
MN103SFJ9D [DX3003]
MN103SFK1K@LQFP80 [DX3017]
MN101EF32D@QFP64 [DX3013]
MN101EF57G [DX3017]
MN103SFA7K@LQFP80 [DX3017]
MN103SFC2DXW [DX3003]
MN103SFH9G [DX3043]
MN103SFJ9DXW [DX3003]

PARAGON

E(E)PROM/FRAM/NVRAM

BN25F04A@SOP8 [DX1044#1]
PN24C02B@SOP8 [DX1045]
PN24C02B@SOT23 [DX1041]
PN24C02B@TSSOP8 [DX1059]
PN24C04A@SOP8 [DX1045]
PN24C04A@TSSOP8 [DX1059]
PN24C08A@SOP8 [DX1045]
PN24C08A@TSSOP8 [DX1059]
PN24C1024A@SOP8 [DX1045]
PN24C1024A@TSSOP8 [DX1059]
PN24C128A@SOP8 [DX1045]
PN24C128A@TSSOP8 [DX1059]
PN24C16A@SOP8 [DX1045]
PN24C16A@TSSOP8 [DX1059]
PN24C256A@SOP8 [DX1045]
PN24C256A@TSSOP8 [DX1059]
PN24C32A@SOP8 [DX1045]
PN24C32A@TSSOP8 [DX1059]
PN24C512A@SOP8 [DX1045]
PN24C512A@TSSOP8 [DX1059]
PN24C64A@SOP8 [DX1045]
PN24C64A@TSSOP8 [DX1059]
PN25F04A@SOP8 [DX1044#1]
PN25F04A@TSSOP8 [DX1045#1]
PN25F08@SOP8[150 mil] [DX1045#1]
PN25F08@SOP8[208 mil] [DX1044#1]
PN25F08@TSSOP8 [DX1000#1]
PN25F16@SOP8[150 mil] [DX1045#1]
PN25F16@SOP8[208 mil] [DX1044#1]
PN25F16@TSSOP8 [DX1000#1]
PN25F32@SOP8 [DX1044#1]

PARALLAX

MICROCONTROLLER

SX20AC/SS/G@SSOP20 [DX1026]
SX20AC/SS@SSOP20 [DX1026]
SX28AC/DP [DX0001]
SX28AC/DP/G [DX0001]
SX28AC/SS/G@SSOP28 [DX1026]
SX28AC/SS@SSOP28 [DX1026]
SX48BD/G@TQFP48 [DX3047]
SX48BD@TQFP48 [DX3047]

PCT

E(E)PROM/FRAM/NVRAM

PCT25LF010@SOIC8(4.0) [DX1045-1]
PCT25LF010@SOIC8(5.4) [DX1044-1]
PCT25LF010@WSON8 [DX4005-1]
PCT25LF010A@SOIC8(4.0) [DX1045-1]
PCT25LF010A@SOIC8(5.4) [DX1044-1]
PCT25LF010A@WSON8 [DX4005-1]
PCT25LF016A@SOIC8(4.0) [DX1045#1]
PCT25LF016A@SOIC8(5.4) [DX1044#1]
PCT25LF016A@WSON8 [DX4005#1]
PCT25LF016B@SOIC8(4.0) [DX1045#1]
PCT25LF016B@SOIC8(5.4) [DX1044#1]
PCT25LF016B@WSON8 [DX4005#1]
PCT25LF020@SOIC8(4.0) [DX1045-1]
PCT25LF020@SOIC8(5.4) [DX1044-1]
PCT25LF020@WSON8 [DX4005-1]

PCT25LF020A@SOIC8(4.0) [DX1045-1]
PCT25LF020A@SOIC8(5.4) [DX1044-1]
PCT25LF020A@WSON8 [DX4005-1]
PCT25LF040@SOIC8(4.0) [DX1045-1]
PCT25LF040@SOIC8(5.4) [DX1044-1]
PCT25LF040@WSON8 [DX4005-1]
PCT25LF040A@SOIC8(4.0) [DX1045-1]
PCT25LF040A@SOIC8(5.4) [DX1044-1]
PCT25LF040A@WSON8 [DX4005-1]
PCT25LF080@SOIC8(4.0) [DX1045-1]
PCT25LF080@SOIC8(5.4) [DX1044-1]
PCT25LF080@WSON8 [DX4005-1]
PCT25LF080A@SOIC8(4.0) [DX1045-1]
PCT25LF080A@SOIC8(5.4) [DX1044-1]
PCT25LF080A@WSON8 [DX4005-1]
PCT25VF010@SOIC8(4.0) [DX1045-1]
PCT25VF010@SOIC8(5.4) [DX1044-1]
PCT25VF010@WSON8 [DX4005-1]
PCT25VF010A@SOIC8(4.0) [DX1045-1]
PCT25VF010A@SOIC8(5.4) [DX1044-1]
PCT25VF010A@WSON8 [DX4005-1]
PCT25VF016B@SOIC8(4.0) [DX1045#1]
PCT25VF016B@SOIC8(5.4) [DX1044#1]
PCT25VF016B@WSON8 [DX4005#1]
PCT25VF020@SOIC8(4.0) [DX1045-1]
PCT25VF020@SOIC8(5.4) [DX1044-1]
PCT25VF020@WSON8 [DX4005-1]
PCT25VF020B@SOIC8(4.0) [DX1045#1]
PCT25VF020B@SOIC8(5.4) [DX1044#1]
PCT25VF020B@WSON8 [DX4005#1]
PCT25VF032B@SOIC16 [DX1033#1]
PCT25VF032B@SOIC8(4.0) [DX1045#1]
PCT25VF032B@SOIC8(5.4) [DX1044#1]
PCT25VF032B@WSON8 [DX4005#1]
PCT25VF040@SOIC8(4.0) [DX1045-1]
PCT25VF040@SOIC8(5.4) [DX1044-1]
PCT25VF040@WSON8 [DX4005-1]
PCT25VF040B@SOIC8(4.0) [DX1045#1]
PCT25VF040B@SOIC8(5.4) [DX1044#1]
PCT25VF040B@WSON8 [DX4005#1]
PCT25VF080@SOIC8(4.0) [DX1045-1]
PCT25VF080@SOIC8(5.4) [DX1044-1]
PCT25VF080@WSON8 [DX4005-1]
PCT25VF080B@SOIC8(4.0) [DX1045#1]
PCT25VF080B@SOIC8(5.4) [DX1044#1]
PCT25VF080B@WSON8 [DX4005#1]
PCT25VF512@SOIC8(4.0) [DX1045-1]
PCT25VF512@SOIC8(5.4) [DX1044-1]
PCT25VF512@WSON8 [DX4005-1]
PCT25VF512A@SOIC8(4.0) [DX1045-1]
PCT25VF512A@SOIC8(5.4) [DX1044-1]
PCT25VF512A@WSON8 [DX4005-1]
PCT25WF010@SOIC8(4.0) [DX1045-1]
PCT25WF010@SOIC8(5.4) [DX1044-1]
PCT25WF010@WSON8 [DX4005-1]
PCT25WF020@SOIC8(4.0) [DX1045-1]
PCT25WF020@SOIC8(5.4) [DX1044-1]
PCT25WF020@WSON8 [DX4005-1]
PCT25WF040@SOIC8(4.0) [DX1045-1]
PCT25WF040@SOIC8(5.4) [DX1044-1]
PCT25WF040@WSON8 [DX4005-1]
PCT25WF080@SOIC8(4.0) [DX1045-1]
PCT25WF080@SOIC8(5.4) [DX1044-1]
PCT25WF080@WSON8 [DX4005-1]
PCT25WF512@SOIC8(4.0) [DX1045-1]
PCT25WF512@SOIC8(5.4) [DX1044-1]
PCT25WF512@WSON8 [DX4005-1]

PHILIPS

E(E)PROM/FRAM/NVRAM

27C010 [DX0001]
27C010@PLCC32 [DX2032]
27C010@TSOP32 [DX1002]
27C040 [DX0001]
27C040@PLCC32 [DX2032]
27C040@TSOP32 [DX1002]
27C210 [DX0001]
27C210@PLCC44 [DX2044]
27C240 [DX0001]
27C240@PLCC44 [DX2044]
27C256 [DX0001]
27C256@PLCC32
27C32 [DX0001]
27C512 [DX0001]
27C512@PLCC32
27C64 [DX0001]
27C64@PLCC32 [DX2032]
27C64A [DX0001]
27C64A@PLCC32 [DX2032]
27C64AF [DX0001]
27C64AF@PLCC32 [DX2032]
27HC641 [DX0001]
27HC641@PLCC28
27PC32 [DX0001]
PCA24S08@SOIC8 [DX1045]
PCA24S08@TSSOP8 [DX1000]
PCA8574(P) [DX0001]
PCA8574(T)@SOIC16 [DX1033]
PCA8574(TS)@SSOP20 [DX1000]
PCA8574A(P) [DX0001]
PCA8574A(T)@SOIC16 [DX1033]
PCA8574A(TS)@SSOP20 [DX1000]
PCA8581 [DX0001]
PCA8581@SOIC8 [DX1045]
PCA8581C [DX0001]
PCA8581C@SOIC8 [DX1045]
PCA8582A [DX0001]
PCA8582A@SOIC8 [DX1045]
PCA8582B [DX0001]
PCA8582B@SOIC8 [DX1045]
PCA8582C [DX0001]
PCA8582C@SOIC8 [DX1045]
PCA8582D [DX0001]
PCA8582D@SOIC8 [DX1045]
PCA8582E [DX0001]
PCA8582E@SOIC8 [DX1045]
PCA9500@HQVFN16 [DX4009]
PCA9500@SOIC16 [DX1033]
PCA9500@TSSOP16 [DX1000]
PCA9501@HQVFN20
PCA9501@SOIC20 [DX1033]
PCA9501@TSSOP20 [DX1000]
PCD8581 [DX0001]
PCD8581@SOIC8 [DX1045]
PCD8581C [DX0001]
PCD8581C@SOIC8 [DX1045]
PCD8582A [DX0001]
PCD8582A@SOIC8 [DX1045]
PCD8582B [DX0001]
PCD8582B@SOIC8 [DX1045]
PCD8582C [DX0001]
PCD8582C@SOIC8 [DX1045]
PCD8582D [DX0001]
PCD8582D@SOIC8 [DX1045]
PCD8582E [DX0001]
PCD8582E@SOIC8 [DX1045]
PCF85102C [DX0001]
PCF85102C@SOIC8 [DX1045]
PCF85103C [DX0001]
PCF85103C@SOIC8 [DX1045]
PCF85116 [DX0001]
PCF85116@SOIC8 [DX1045]
PCF8581 [DX0001]
PCF8581@SOIC8 [DX1045]
PCF8581C [DX0001]
PCF8581C@SOIC8 [DX1045]
PCF8582A [DX0001]
PCF8582A@SOIC8 [DX1045]
PCF8582B [DX0001]
PCF8582B@SOIC8 [DX1045]
PCF8582C [DX0001]
PCF8582C@SOIC8 [DX1045]
PCF8582D [DX0001]
PCF8582D@SOIC8 [DX1045]
PCF8582E [DX0001]
PCF8582E@SOIC8 [DX1045]
PCF8594 [DX0001]
PCF8594@SOIC8 [DX1045]
PCF8594C [DX0001]
PCF8594C@SOIC8 [DX1045]
PCF8594D [DX0001]
PCF8594D@SOIC8 [DX1045]

PCF8594E [DX0001]
PCF8594E@SOIC8 [DX1045]
PCF8598 [DX0001]
PCF8598@SOIC8 [DX1044]
PCF8598C [DX0001]
PCF8598C@SOIC8 [DX1044]
PCF8598D [DX0001]
PCF8598D@SOIC8 [DX1044]
PCF8598E [DX0001]
PCF8598E@SOIC8 [DX1044]

BPROM

82S126 [DX0001]
82S126A [DX0001]
82S129 [DX0001]
82S129A [DX0001]
82S130 [DX0001]
82S130A [DX0001]
82S131 [DX0001]
82S131A [DX0001]
82S140 [DX0001]
82S141 [DX0001]
82S191 [DX0001]
82S191A [DX0001]
82S191B [DX0001]
82S191C [DX0001]
N82LS135 [DX0001]
N82LS135@PLCC20 [DX2020]
N82S123 [DX0001]
N82S123A [DX0001]
N82S135 [DX0001]
N82S135@PLCC20 [DX2020]
N82S136 [DX0001]
N82S137 [DX0001]
N82S137A [DX0001]
N82S137B [DX0001]
N82S137C [DX0001]
N82S146 [DX0001]
N82S146@PLCC20 [DX2020]
N82S147 [DX0001]
N82S147@PLCC20 [DX2020]
N82S147A [DX0001]
N82S147A@PLCC20 [DX2020]
N82S147B [DX0001]
N82S147B@PLCC20 [DX2020]
N82S167 [DX0001]
N82S23 [DX0001]
N82S23A [DX0001]

PLD

82S105 [DX0001]
82S105@PLCC28 [DX2028]
82S152 [DX0001]
82S152@PLCC20 [DX2020]
82S153 [DX0001]
82S153@PLCC20 [DX2020]
82S155 [DX0001]
82S155@PLCC20 [DX2020]
82S157 [DX0001]
82S157@PLCC20 [DX2020]
82S159 [DX0001]
82S159@PLCC20 [DX2020]
82S167 [DX0001]
82S167@PLCC28 [DX2028]
82S168 [DX0001]
82S168@PLCC28 [DX2028]
82S173 [DX0001]
82S173@PLCC28 [DX2028]
82S179 [DX0001]
82S179@PLCC28 [DX2028]
PLC18V8Z [DX0001]
PLC18V8Z@PLCC20 [DX2020]
PLC18V8ZI [DX0001]
PLC18V8ZI@PLCC20 [DX2020]
PLS104 [DX0001]
PLS104@PLCC28 [DX2028]
PLS104A [DX0001]
PLS104A@PLCC28 [DX2028]
PLS105 [DX0001]
PLS105@PLCC28 [DX2028]
PLS105A [DX0001]
PLS105A@PLCC28 [DX2028]
PLS152 [DX0001]
PLS152@PLCC20 [DX2020]

PLS153 [DX0001]
PLS153A [DX0001]
PLS155 [DX0001]
PLS157 [DX0001]
PLS159 [DX0001]
PLS159A [DX0001]
PLS167 [DX0001]
PLS167A [DX0001]
PLS168 [DX0001]
PLS168A [DX0001]
PLS173 [DX0001]
PLS179 [DX0001]
PZ3032@PLCC44 [DX2044]
PZ3032CS@PLCC44 [DX2044]
PZ3064@PLCC44 [DX2044]
PZ3064@PLCC84 [DX2084]
PZ3064@TQFP44 [DX3003]
PZ3128@PQFP100 [DX3022]
PZ5032@PLCC44 [DX2044]
PZ5032CS@PLCC44 [DX2044]
PZ5064@PLCC44 [DX2044]
PZ5064@PLCC84 [DX2084]
PZ5064@TQFP44 [DX3003]
PZ5128@PQFP100 [DX3022]
PLS153@PLCC20 [DX2020]
PLS153A@PLCC20 [DX2020]
PLS155@PLCC20 [DX2020]
PLS157@PLCC20 [DX2020]
PLS159@PLCC20 [DX2020]
PLS159A@PLCC20 [DX0001]
PLS167@PLCC28 [DX2028]
PLS167A@PLCC28 [DX2028]
PLS168@PLCC28 [DX2028]
PLS168A@PLCC28 [DX2028]
PLS173@PLCC28 [DX2028]
PLS179@PLCC28 [DX2028]
PZ3032@TQFP44 [DX3003]
PZ3032CS@TQFP44 [DX3003]
PZ3064@PLCC68 [DX2068]
PZ3064@PQFP100 [DX3022]
PZ3128@PLCC84 [DX2084]
PZ3128@TQFP100 [DX3021]
PZ5032@TQFP44 [DX3003]
PZ5032CS@TQFP44 [DX3003]
PZ5064@PLCC68 [DX2068]
PZ5064@PQFP100 [DX3022]
PZ5128@PLCC84 [DX2084]
PZ5128@TQFP100 [DX3021]

MICROCONTROLLER

61B0700 [DX1001]
61E0700 [DX1001]
LPC1111/101@QFN33 [DX4016]
LPC1111/102@LQFP48 [DX3007]
LPC1111/102@QFP44 [DX3005]
LPC1111/103@QFN33 [DX4016]
LPC1111/201@LQFP48 [DX3007]
LPC1111/201@QFP44 [DX3005]
LPC1111/202@QFN33 [DX4016]
LPC1111/203@LQFP48 [DX3007]
LPC1111/203@QFP44 [DX3005]
LPC1111@QFN33 [DX4016]
LPC1111FHI33/303 [DX4015]
LPC1112/101@LQFP48 [DX3007]
LPC1112/101@QFP44 [DX3005]
LPC1112/102@QFN33 [DX4016]
LPC1112/103@LQFP48 [DX3007]
LPC1112/103@QFP44 [DX3005]
LPC1112/201@QFN33 [DX4016]
LPC1112/202@LQFP48 [DX3007]
61C0700 [DX1001]
LPC1111/101@LQFP48 [DX3007]
LPC1111/101@QFP44 [DX3005]
LPC1111/102@QFN33 [DX4016]
LPC1111/103@LQFP48 [DX3007]
LPC1111/103@QFP44 [DX3005]
LPC1111/201@QFN33 [DX4016]
LPC1111/202@LQFP48 [DX3007]
LPC1111/202@QFP44 [DX3005]
LPC1111/203@QFN33 [DX4016]
LPC1111@LQFP48 [DX3007]
LPC1111@QFP44 [DX3005]
LPC1111FHN33/203 [DX4016]
LPC1112/101@QFN33 [DX4016]
LPC1112/102@LQFP48 [DX3007]
LPC1112/102@QFP44 [DX3005]
LPC1112/103@QFN33 [DX4016]
LPC1112/201@LQFP48 [DX3007]
LPC1112/201@QFP44 [DX3005]
LPC1112/202@QFN33 [DX4016]

LPC1112/202@QFP44 [DX3005]
LPC1112/203@QFN33 [DX4016]
LPC1112@LQFP48 [DX3007]
LPC1112@QFP44 [DX3005]
LPC1112FHN33/203 [DX4016]
LPC1113/101@QFN33 [DX4016]
LPC1113/102@LQFP48 [DX3007]
LPC1113/102@QFP44 [DX3005]
LPC1113/103@QFN33 [DX4016]
LPC1113/201@LQFP48 [DX3007]
LPC1113/201@QFP44 [DX3005]
LPC1113/202@QFN33 [DX4016]
LPC1113/203@LQFP48 [DX3007]
LPC1113/203@QFP44 [DX3005]
LPC1113/301@QFP44 [DX3005]
LPC1113/302@QFN33 [DX4016]
LPC1113/302@QFP48 [DX3007]
LPC1113/303@QFP44 [DX3005]
LPC1113@LQFP48 [DX3007]
LPC1113@QFP44 [DX3005]
LPC1113FHN33/203 [DX4016]
LPC1114/101@QFN33 [DX4016]
LPC1114/102@LQFP48 [DX3007]
LPC1114/102@QFP44 [DX3005]
LPC1114/103@QFN33 [DX4016]
LPC1114/201@LQFP48 [DX3007]
LPC1114/201@QFP44 [DX3005]
LPC1114/202@QFN33 [DX4016]
LPC1114/203@LQFP48 [DX3007]
LPC1114/203@QFP44 [DX3005]
LPC1114/301@QFP44 [DX3005]
LPC1114/302@QFN33 [DX4016]
LPC1114/302@QFP48 [DX3007]
LPC1114/303@QFP44 [DX3005]
LPC1114/323@QFN33 [DX4016]
LPC1114/323@QFP48 [DX3007]
LPC1114/333@QFP44 [DX3005]
LPC1114@LQFP48 [DX3007]
LPC1114@QFP44 [DX3005]
LPC1114FHN33/203 [DX4016]
LPC11A11/001@QFN33 [DX4016]
LPC11A12/101@QFN33 [DX4016]
LPC11A13/201@QFN33 [DX4016]
LPC11A14/301@QFN33 [DX4016]
LPC11C12/101@LQFP48 [DX3007]
LPC11C12/103@LQFP48 [DX3007]
LPC11C12/202@LQFP48 [DX3007]
LPC11C12/301@LQFP48 [DX3007]
LPC1112/203@LQFP48 [DX3007]
LPC1112/203@QFP44 [DX3005]
LPC1112@QFN33 [DX4016]
LPC1112FHI33/303 [DX4015]
LPC1113/101@LQFP48 [DX3007]
LPC1113/101@QFP44 [DX3005]
LPC1113/102@QFN33 [DX4016]
LPC1113/103@LQFP48 [DX3007]
LPC1113/103@QFP44 [DX3005]
LPC1113/201@QFN33 [DX4016]
LPC1113/202@LQFP48 [DX3007]
LPC1113/202@QFP44 [DX3005]
LPC1113/203@QFN33 [DX4016]
LPC1113/301@QFN33 [DX4016]
LPC1113/301@QFP48 [DX3007]
LPC1113/302@QFP44 [DX3005]
LPC1113/303@QFN33 [DX4016]
LPC1113/303@QFP48 [DX3007]
LPC1113@QFN33 [DX4016]
LPC1113FHI33/303 [DX4015]
LPC1114/101@LQFP48 [DX3007]
LPC1114/101@QFP44 [DX3005]
LPC1114/102@QFN33 [DX4016]
LPC1114/103@LQFP48 [DX3007]
LPC1114/103@QFP44 [DX3005]
LPC1114/201@QFN33 [DX4016]
LPC1114/202@LQFP48 [DX3007]
LPC1114/202@QFP44 [DX3005]
LPC1114/203@QFN33 [DX4016]
LPC1114/301@QFN33 [DX4016]
LPC1114/301@QFP48 [DX3007]
LPC1114/302@QFP44 [DX3005]
LPC1114/303@QFN33 [DX4016]
LPC1114/303@QFP48 [DX3007]
LPC1114/323@QFP44 [DX3005]
LPC1114/333@QFN33 [DX4016]
LPC1114/333@QFP48 [DX3007]
LPC1114@QFN33 [DX4016]
LPC1114FHI33/303 [DX4015]
LPC1115/303@QFP48 [DX3007]
LPC11A11/001@QFP48 [DX3007]
LPC11A12/101@QFP48 [DX3007]
LPC11A13/201@QFP48 [DX3007]
LPC11A14/301@QFP48 [DX3007]
LPC11C12/102@LQFP48 [DX3007]
LPC11C12/201@LQFP48 [DX3007]
LPC11C12/203@LQFP48 [DX3007]
LPC11C12@LQFP48 [DX3007]

LPC11C14/101@LQFP48 [DX3007]
LPC11C14/102@LQFP48 [DX3007]
LPC11C14/103@LQFP48 [DX3007]
LPC11C14/201@LQFP48 [DX3007]
LPC11C14/202@LQFP48 [DX3007]
LPC11C14/203@LQFP48 [DX3007]
LPC11C14/301@LQFP48 [DX3007]
LPC11C14@LQFP48 [DX3007]
LPC11C22/101@LQFP48 [DX3007]
LPC11C22/102@LQFP48 [DX3007]
LPC11C22/103@LQFP48 [DX3007]
LPC11C22/201@LQFP48 [DX3007]
LPC11C22/202@LQFP48 [DX3007]
LPC11C22/203@LQFP48 [DX3007]
LPC11C22/301@LQFP48 [DX3007]
LPC11C22@LQFP48 [DX3007]
LPC11C24/101@LQFP48 [DX3007]
LPC11C24/102@LQFP48 [DX3007]
LPC11C24/103@LQFP48 [DX3007]
LPC11C24/201@LQFP48 [DX3007]
LPC11C24/202@LQFP48 [DX3007]
LPC11C24/203@LQFP48 [DX3007]
LPC11C24/301@LQFP48 [DX3007]
LPC11C24@LQFP48 [DX3007]
LPC11D14FBD100 [DX3043]
LPC11E11FHI33101 [DX4015]
LPC11E12@QFN33 [DX4016]
LPC11E12@QFP48 [DX3007]
LPC11E12@TFBGA48 [BBBB]
LPC11E13/301@QFP64 [DX3011]
LPC11E13/401@QFP64 [DX3011]
LPC11E13@QFN33 [DX4016]
LPC11E13@QFP48 [DX3007]
LPC11E13@QFP64 [DX3011]
LPC11E13@TFBGA48 [BBBB]
LPC11E14/301@QFP64 [DX3011]
LPC11E14/401@QFP64 [DX3011]
LPC11E14@QFN33 [DX4016]
LPC11E14@QFP48 [DX3007]
LPC11E14@QFP64 [DX3011]
LPC11E14@TFBGA48 [BBBB]
LPC11E23/301@QFN33 [DX4016]
LPC11E23/301@QFP48 [DX3007]
LPC11E23/301@QFP64 [DX3011]
LPC11E23/301@TFBGA48 [BBBB]
LPC11E23/401@QFN33 [DX4016]
LPC11E23/401@QFP48 [DX3007]
LPC11E23/401@QFP64 [DX3011]
LPC11E23/401@TFBGA48 [BBBB]
LPC11E23@QFN33 [DX4016]
LPC11E23@QFP48 [DX3007]
LPC11E23@QFP64 [DX3011]
LPC11E23@TFBGA48 [BBBB]
LPC11E24/301@QFN33 [DX4016]
LPC11E24/301@QFP48 [DX3007]
LPC11E24/301@QFP64 [DX3011]
LPC11E24/301@TFBGA48 [BBBB]
LPC11E24/401@QFN33 [DX4016]
LPC11E24/401@QFP48 [DX3007]
LPC11E24/401@QFP64 [DX3011]
LPC11E24/401@TFBGA48 [BBBB]
LPC11E24@QFN33 [DX4016]
LPC11E24@QFP48 [DX3007]
LPC11E24@QFP64 [DX3011]
LPC11E24@TFBGA48 [BBBB]
LPC11U12@QFN33 [DX4016]
LPC11U12@QFP48 [DX3007]
LPC11U12@TFBGA48 [BBBB]
LPC11U13@QFN33 [DX4016]
LPC11U13@QFP48 [DX3007]
LPC11U13@TFBGA48 [BBBB]
LPC11U14@QFN33 [DX4016]
LPC11U14@QFP48 [DX3007]
LPC11U14@TFBGA48 [BBBB]
LPC11U23/301@QFN33 [DX4016]
LPC11U23/301@QFP48 [DX3007]
LPC11U23/301@QFP64 [DX3011]
LPC11U23/301@TFBGA48 [BBBB]
LPC11U23/401@QFN33 [DX4016]
LPC11U23/401@QFP48 [DX3007]
LPC11U23/401@QFP64 [DX3011]
LPC11U23/401@TFBGA48 [BBBB]
LPC11U23@QFN33 [DX4016]
LPC11U23@QFP48 [DX3007]
LPC11U23@QFP64 [DX3011]
LPC11U23@TFBGA48 [BBBB]
LPC11U24/301@QFN33 [DX4016]
LPC11U24/301@QFP48 [DX3007]
LPC11U24/301@QFP64 [DX3011]
LPC11U24/301@TFBGA48 [BBBB]
LPC11U24/401@QFN33 [DX4016]
LPC11U24/401@QFP48 [DX3007]
LPC11U24/401@QFP64 [DX3011]
LPC11U24/401@TFBGA48 [BBBB]
LPC11U24@QFN33 [DX4016]
LPC11U24@QFP48 [DX3007]

LPC11U24@QFP64 [DX3011]
LPC11U24@TFBGA48 [BBBB]
LPC11U33@QFN33 [DX4016]
LPC11U34/311@QFN33 [DX4016]
LPC11U34/421@QFN33 [DX4016]
LPC11U35/301@BGA48 [BBBB]
LPC11U35/301@QFP48 [DX3007]
LPC11U35/301@QFP64 [DX3011]
LPC11U35/401@BGA48 [BBBB]
LPC11U35/401@QFP48 [DX3007]
LPC11U35/401@QFP64 [DX3011]
LPC11U35/501@BGA48 [BBBB]
LPC11U35/501@QFP48 [DX3007]
LPC11U35/501@QFP64 [DX3011]
LPC11U35FHI33401 [DX4015]
LPC11U35FHI33501 [DX4015]
LPC11U36/301@BGA48 [BBBB]
LPC11U36/301@QFP48 [DX3007]
LPC11U36/301@QFP64 [DX3011]
LPC11U36/401@BGA48 [BBBB]
LPC11U36/401@QFP48 [DX3007]
LPC11U36/401@QFP64 [DX3011]
LPC11U36/501@BGA48 [BBBB]
LPC11U36/501@QFP48 [DX3007]
LPC11U36/501@QFP64 [DX3011]
LPC11U37/301@BGA48 [BBBB]
LPC11U37/301@QFP48 [DX3007]
LPC11U37/301@QFP64 [DX3011]
LPC11U37/401@BGA48 [BBBB]
LPC11U37/401@QFP48 [DX3007]
LPC11U37/401@QFP64 [DX3011]
LPC11U37/501@BGA48 [BBBB]
LPC11U37/501@QFP48 [DX3007]
LPC11U37/501@QFP64 [DX3011]
LPC1224/101@LQFP48 [DX3007]
LPC1224/101@LQFP64 [DX3011]
LPC1224/121@LQFP48 [DX3007]
LPC1224/121@LQFP64 [DX3011]
LPC1224/201@LQFP48 [DX3007]
LPC1224/201@LQFP64 [DX3011]
LPC1224/221@LQFP48 [DX3007]
LPC1224/221@LQFP64 [DX3011]
LPC1225/201@LQFP48 [DX3007]
LPC1225/201@LQFP64 [DX3011]
LPC1225/221@LQFP48 [DX3007]
LPC1225/221@LQFP64 [DX3011]
LPC1225/301@LQFP48 [DX3007]
LPC1225/301@LQFP64 [DX3011]
LPC1225/321@LQFP48 [DX3007]
LPC1225/321@LQFP64 [DX3011]
LPC1226/201@LQFP48 [DX3007]
LPC1226/201@LQFP64 [DX3011]
LPC1226/301@LQFP48 [DX3007]
LPC1226/301@LQFP64 [DX3011]
LPC1227/201@LQFP48 [DX3007]
LPC1227/201@LQFP64 [DX3011]
LPC1227/301@LQFP48 [DX3007]
LPC1227/301@LQFP64 [DX3011]
LPC12D27/201@LQFP100 [DX3043]
LPC12D27/201@LQFP48 [DX3007]
LPC12D27/201@LQFP64 [DX3011]
LPC12D27/301@LQFP100 [DX3043]
LPC12D27/301@LQFP48 [DX3007]
LPC12D27/301@LQFP64 [DX3011]
LPC1311@LQFP48 [DX3007]
LPC1311@QFN33 [DX4016]
LPC1312@LQFP48 [DX3007]
LPC1312@QFN33 [DX4016]
LPC1313@LQFP48 [DX3007]
LPC1313@QFN33 [DX4016]
LPC1314@LQFP48 [DX3007]
LPC1314@QFN33 [DX4016]
LPC1315FBD48 [DX3007]
LPC1315FHN33 [DX4016]
LPC1316FBD48 [DX3007]
LPC1316FHN33 [DX4016]
LPC1317FBD48 [DX3007]
LPC1317FBD64 [DX3011]
LPC1317FHN33 [DX4016]
LPC1341@LQFP48 [DX3007]
LPC1341@QFN33 [DX4016]
LPC1342@LQFP48 [DX3007]
LPC1342@QFN33 [DX4016]
LPC1343@LQFP48 [DX3007]
LPC1343@QFN33 [DX4016]
LPC1344@LQFP48 [DX3007]
LPC1344@QFN33 [DX4016]
LPC1345FBD48 [DX3007]
LPC1345FHN33 [DX4016]
LPC1346FBD48 [DX3007]
LPC1346FHN33 [DX4016]
LPC1347FBD48 [DX3007]
LPC1347FBD64 [DX3011]
LPC1347FHN33 [DX4016]
LPC1751@LQFP80 [DX3016]
LPC1752@LQFP80 [DX3016]

LPC1754@LQFP80 [DX3016]
LPC1756@LQFP80 [DX3016]
LPC1758@LQFP80 [DX3016]
LPC1759@LQFP80 [DX3016]
LPC1763@LQFP100 [DX3043]
LPC1763FET100 [DX5055]
LPC1764@LQFP100 [DX3043]
LPC1764FET100 [DX5055]
LPC1765@LQFP100 [DX3043]
LPC1765FET100 [DX5055]
LPC1766@LQFP100 [DX3043]
LPC1766FET100 [DX5055]
LPC1767@LQFP100 [DX3043]
LPC1767FET100 [DX5055]
LPC1768@LQFP100 [DX3043]
LPC1768FET100 [DX5055]
LPC1769@LQFP100 [DX3043]
LPC1769FET100 [DX5055]
LPC1774FBD144 [DX3051]
LPC1774FBD208 [DX3092]
LPC1774FET180 [BBBB]
LPC1774FET208 [BBBB]
LPC1775FBD144 [DX3051]
LPC1775FBD208 [DX3092]
LPC1775FET180 [BBBB]
LPC1775FET208 [BBBB]
LPC1776FBD144 [DX3051]
LPC1776FBD208 [DX3092]
LPC1776FET180 [BBBB]
LPC1776FET208 [BBBB]
LPC1777FBD144 [DX3051]
LPC1777FBD208 [DX3092]
LPC1777FET180 [BBBB]
LPC1777FET208 [BBBB]
LPC1778FBD144 [DX3051]
LPC1778FBD208 [DX3092]
LPC1778FET180 [BBBB]
LPC1778FET208 [BBBB]
LPC1784FBD144 [DX3051]
LPC1784FBD208 [DX3092]
LPC1784FET180 [BBBB]
LPC1784FET208 [BBBB]
LPC1785FBD144 [DX3051]
LPC1785FBD208 [DX3092]
LPC1785FET180 [BBBB]
LPC1785FET208 [BBBB]
LPC1786FBD144 [DX3051]
LPC1786FBD208 [DX3092]
LPC1786FET180 [BBBB]
LPC1786FET208 [BBBB]
LPC1787FBD144 [DX3051]
LPC1787FBD208 [DX3092]
LPC1787FET180 [BBBB]
LPC1787FET208 [BBBB]
LPC1788FBD144 [DX3051]
LPC1788FBD208 [DX3092]
LPC1788FET180 [BBBB]
LPC1788FET208 [BBBB]
LPC1827FBD144 [DX3051]
LPC2101FBD48/00@LQFP48 [DX3007]
LPC2101FBD48/01@LQFP48 [DX3007]
LPC2101FBD48@LQFP48 [DX3007]
LPC2101FHN48/00@HVQFN48 [DX4021]
LPC2101FHN48/01@HVQFN48 [DX4021]
LPC2101FHN48@HVQFN48 [DX4021]
LPC2102FBD48/00@LQFP48 [DX3007]
LPC2102FBD48/01@LQFP48 [DX3007]
LPC2102FBD48@LQFP48 [DX3007]
LPC2102FHN48/00@HVQFN48 [DX4021]
LPC2102FHN48/01@HVQFN48 [DX4021]
LPC2102FHN48@HVQFN48 [DX4021]
LPC2103FA44@PLCC44 [DX2144]
LPC2103FBD48/00@LQFP48 [DX3007]
LPC2103FBD48/01@LQFP48 [DX3007]
LPC2103FBD48@LQFP48 [DX3007]
LPC2103FHN48/00@HVQFN48 [DX4021]
LPC2103FHN48/01@HVQFN48 [DX4021]
LPC2103FHN48@HVQFN48 [DX4021]
LPC2104BBD48@LQFP48 [DX3007]
LPC2104FBD48/00@LQFP48 [DX3007]
LPC2104FBD48/01@LQFP48 [DX3007]
LPC2104FBD48@LQFP48 [DX3007]
LPC2104FHN48/00@HVQFN48 [DX4021]
LPC2104FHN48/01@HVQFN48 [DX4021]
LPC2104FHN48@HVQFN48 [DX4021]
LPC2105BBD48@LQFP48 [DX3007]
LPC2105FBD48/00@LQFP48 [DX3007]
LPC2105FBD48/01@LQFP48 [DX3007]
LPC2105FBD48@LQFP48 [DX3007]
LPC2105FHN48/00@HVQFN48 [DX4021]
LPC2105FHN48/01@HVQFN48 [DX4021]
LPC2105FHN48@HVQFN48 [DX4021]
LPC2106BBD48@LQFP48 [DX3007]
LPC2106FBD48/00@LQFP48 [DX3007]
LPC2106FBD48/01@LQFP48 [DX3007]
LPC2106FBD48@LQFP48 [DX3007]

LPC2106FHN48/00@HVQFN48 [DX4021]
LPC2106FHN48/01@HVQFN48 [DX4021]
LPC2106FHN48@HVQFN48 [DX4021]
LPC2109FBD64@LQFP64 [DX3011]
LPC2109FHN64@QFN64 [DX4023]
LPC2114FBD64@LQFP64 [DX3011]
LPC2114FHN64@QFN64 [DX4023]
LPC2119FBD64@LQFP64 [DX3011]
LPC2119FHN64@QFN64 [DX4023]
LPC2124FBD64@LQFP64 [DX3011]
LPC2124FHN64@QFN64 [DX4023]
LPC2129FBD64@LQFP64 [DX3011]
LPC2129FHN64@QFN64 [DX4023]
LPC2131FBD64@LQFP64 [DX3011]
LPC2131FHN64@QFN64 [DX4023]
LPC2132FBD64@LQFP64 [DX3011]
LPC2132FHN64@QFN64 [DX4023]
LPC2134FBD64@LQFP64 [DX3011]
LPC2134FHN64@QFN64 [DX4023]
LPC2136FBD64@LQFP64 [DX3011]
LPC2136FHN64@QFN64 [DX4023]
LPC2138FBD64@LQFP64 [DX3011]
LPC2138FHN64@QFN64 [DX4023]
LPC2141FBD64@LQFP64 [DX3011]
LPC2142FBD64@LQFP64 [DX3011]
LPC2144FBD64@LQFP64 [DX3011]
LPC2146FBD64@LQFP64 [DX3011]
LPC2148FBD64@LQFP64 [DX3011]
LPC2194FBD64@LQFP64 [DX3011]
LPC2194FHN64@QFN64 [DX4023]
LPC2212HBD144@LQFP144 [DX3035]
LPC2214FBD144@LQFP144 [DX3035]
LPC2214HBD144@LQFP144 [DX3035]
LPC2292FBD144@LQFP144 [DX3035]
LPC2292HBD144@LQFP144 [DX3035]
LPC2294FBD144@LQFP144 [DX3035]
LPC2294HBD144@LQFP144 [DX3035]
LPC2361@LQFP100 [DX3021]
LPC2361@TFBGA100 [DX5055]
LPC2362@LQFP100 [DX3021]
LPC2362@TFBGA100 [DX5055]
LPC2364@LQFP100 [DX3021]
LPC2364@LQFP100(new) [DX3021]
LPC2364@TFBGA100 [DX5055]
LPC2364@TFBGA100(new) [DX5055]
LPC2365@LQFP100 [DX3021]
LPC2365@TFBGA100 [DX5055]
LPC2366@LQFP100 [DX3021]
LPC2366@LQFP100(new) [DX3021]
LPC2366@TFBGA100 [DX5055]
LPC2366@TFBGA100(new) [DX5055]
LPC2367@LQFP100 [DX3021]
LPC2367@TFBGA100 [DX5055]
LPC2368@LQFP100 [DX3021]
LPC2368@LQFP100(new) [DX3021]
LPC2368@TFBGA100 [DX5055]
LPC2368@TFBGA100(new) [DX5055]
LPC2377@LQFP144 [DX3035]
LPC2378(new)@LQFP144 [DX3035]
LPC2378@LQFP144 [DX3035]
LPC2387@LQFP100 [DX3021]
LPC2387@TFBGA100 [DX5055]
LPC2388@LQFP144 [DX3035]
LPC2458FET180 [DX5213]
LPC2458FET180N [DX5213]
LPC2468FBD208(new)@LQFP208(*) [DX3040]
LPC2468FBD208@LQFP208(*) [DX3040]
LPC2468FET208(new)@BGA208(*) [DX5125]
LPC2468FET208@BGA208(*) [DX5125]
LPC2478FBD208@LQFP208(*) [DX3040]
LPC2478FET208@BGA208(*) [DX5125]
LPC4072FBD144 [DX3051]
LPC4072FBD208 [DX3092]
LPC4072FBD80 [DX3016]
LPC4072FET180 [BBBB]
LPC4072FET208 [DX5253]
LPC4074FBD144 [DX3051]
LPC4074FBD208 [DX3092]
LPC4074FBD80 [DX3016]
LPC4074FET180 [BBBB]
LPC4074FET208 [DX5253]
LPC4076FBD144 [DX3051]
LPC4076FBD208 [DX3092]
LPC4076FBD80 [DX3016]
LPC4076FET180 [BBBB]
LPC4076FET208 [DX5253]
LPC4078FBD144 [DX3051]
LPC4078FBD208 [DX3092]
LPC4078FBD80 [DX3016]
LPC4078FET180 [BBBB]

LPC4078FET208 [DX5253]
LPC4088FBD208 [DX3092]
LPC4088FET180 [BBBB]
OM4371FN [DX0001]
OM4371FN@TQFP44 [DX3005]
P83C660X2@TQFP44 [DX3005]
P83C661X2@TQFP44 [DX3005]
P87C055@SDIP42 [DX0042]
P87C451@SDIP64 [DX0064]
P87C51 [DX0001]
P87C51@TQFP44 [DX3002]
P87C51FA@PLCC44 [DX2044]
P87C51FB [DX0001]
P87C51FB@TQFP44 [DX3002]
P87C51FC@PLCC44 [DX2044]
P87C51MA2@PLCC44 [DX2044]
P87C51MC2@PLCC44 [DX2044]
P87C51RA+@PLCC44 [DX2044]
P87C51RA2 [DX0001]
P87C51RA2@TQFP44 [DX3002]
P87C51RB+@PLCC44 [DX2044]
P87C51RB2 [DX0001]
P87C51RB2@TQFP44 [DX3002]
P87C51RC+@PLCC44 [DX2044]
P87C51RC2 [DX0001]
P87C51RC2@TQFP44 [DX3002]
P87C51RD+@PLCC44 [DX2044]
P87C51RD2 [DX0001]
P87C51RD2@TQFP44 [DX3002]
P87C51SB@PLCC44 [DX2044]
P87C51SF [DX0001]
P87C51SF@TQFP44 [DX3002]
P87C51UB@PLCC44 [DX2044]
P87C51UF [DX0001]
P87C51UF@TQFP44 [DX3002]
P87C51X2@PLCC44 [DX2044]
P87C51X2@TTSOP38 [DX1049]
P87C52@PLCC44 [DX2044]
P87C524 [DX0001]
P87C524@TQFP44 [DX3003]
P87C528@PLCC44 [DX2044]
P87C52SB [DX0001]
P87C52SB@TQFP44 [DX3002]
P87C52SF@PLCC44 [DX2044]
P87C52UB [DX0001]
P87C52UB@TQFP44 [DX3002]
P87C52UF@PLCC44 [DX2044]
P87C52X2 [DX0001]
LPC4088FBD144 [DX3051]
LPC4088FBD80 [DX3016]
LPC4088FET208 [DX5253]
OM4371FN@PLCC44 [DX2044]
P83C660X2@PLCC44 [DX2044]
P83C661X2@PLCC44 [DX2044]
P87C054@SDIP42 [DX0042]
P87C451@PLCC68 [DX2068]
P87C453@PLCC68 [DX2068]
P87C51@PLCC44 [DX2044]
P87C51FA [DX0001]
P87C51FA@TQFP44 [DX3002]
P87C51FB@PLCC44 [DX2044]
P87C51FC [DX0001]
P87C51FC@TQFP44 [DX3003]
P87C51MB2@PLCC44 [DX2044]
P87C51RA+ [DX0001]
P87C51RA+@TQFP44 [DX3003]
P87C51RA2@PLCC44 [DX2044]
P87C51RB+ [DX0001]
P87C51RB+@TQFP44 [DX3003]
P87C51RB2@PLCC44 [DX2044]
P87C51RC+ [DX0001]
P87C51RC+@TQFP44 [DX3003]
P87C51RC2@PLCC44 [DX2044]
P87C51RD+ [DX0001]
P87C51RD+@TQFP44 [DX3003]
P87C51RD2@PLCC44 [DX2044]
P87C51SB [DX0001]
P87C51SB@TQFP44 [DX3002]
P87C51SF@PLCC44 [DX2044]
P87C51UB [DX0001]
P87C51UB@TQFP44 [DX3002]
P87C51UF@PLCC44 [DX2044]
P87C51X2 [DX0001]
P87C51X2@TQFP44 [DX3005]
P87C52 [DX0001]
P87C52@TQFP44 [DX3002]
P87C524@PLCC44 [DX2044]
P87C528 [DX0001]
P87C528@TQFP44 [DX3003]
P87C52SB@PLCC44 [DX2044]
P87C52SF [DX0001]
P87C52SF@TQFP44 [DX3002]
P87C52UB@PLCC44 [DX2044]
P87C52UF [DX0001]
P87C52UF@TQFP44 [DX3002]
P87C52X2@PLCC44 [DX2044]

P87C52X2@TQFP44 [DX3005]
P87C54 [DX0001]
P87C54@TQFP44 [DX3002]
P87C54SB@PLCC44 [DX2044]
P87C54SF [DX0001]
P87C54SF@TQFP44 [DX3002]
P87C54UB@PLCC44 [DX2044]
P87C54UF [DX0001]
P87C54UF@TQFP44 [DX3002]
P87C54X2@PLCC44 [DX2044]
P87C54X2@TTSOP38 [DX1049]
P87C550@PLCC44 [DX2044]
P87C552@PQFP80 [DX3019]
P87C554@PQFP80 [DX3019]
P87C575@PLCC44 [DX2044]
P87C576 [DX0001]
P87C576@TQFP44 [DX3002]
P87C58@PLCC44 [DX2044]
P87C58SB [DX0001]
P87C58SB@TQFP44 [DX3002]
P87C58UB@PLCC44 [DX2044]
P87C58X2 [DX0001]
P87C58X2@TQFP44 [DX3005]
P87C591@PLCC44 [DX2044]
P87C592@PLCC68 [DX2068]
P87C652@PLCC44 [DX2044]
P87C654 [DX0001]
P87C654@TQFP44 [DX3002]
P87C660X2@TQFP44 [DX3005]
P87C661X2@TQFP44 [DX3005]
P87C748@PLCC28 [DX2028]
P87C749@PLCC28 [DX2028]
P87C750@PLCC28 [DX2028]
P87C751 [DX0001]
P87C751@SSOP24 [DX1026]
P87C752@PLCC28 [DX2028]
P87C754 [DX0001]
P87C754@SSOP28 [DX1026]
P87CL52X2@PLCC44 [DX2044]
P87CL52X2@TTSOP38 [DX1049]
P87CL54X2@PLCC44 [DX2044]
P87CL54X2@TTSOP38 [DX1049]
P87L51FA@PLCC44 [DX2044]
P87L51FB [DX0001]
P87L51FB@TQFP44 [DX3002]
P87LPC759(ISP) [DX0001]
P87LPC760(ISP) [DX0001]
P87LPC760@TSSOP14(ISP) [DX0001]
P87C52X2@TTSOP38 [DX1049]
P87C54@PLCC44 [DX2044]
P87C54SB [DX0001]
P87C54SB@TQFP44 [DX3002]
P87C54SF@PLCC44 [DX2044]
P87C54UB [DX0001]
P87C54UB@TQFP44 [DX3002]
P87C54UF@PLCC44 [DX2044]
P87C54X2 [DX0001]
P87C54X2@TQFP44 [DX3005]
P87C550 [DX0001]
P87C552@PLCC68 [DX2068]
P87C554@PLCC68 [DX2068]
P87C575 [DX0001]
P87C575@TQFP44 [DX3002]
P87C576@PLCC44 [DX2044]
P87C58 [DX0001]
P87C58@TQFP44 [DX3002]
P87C58SB@PLCC44 [DX2044]
P87C58UB [DX0001]
P87C58UB@TQFP44 [DX3002]
P87C58X2@PLCC44 [DX2044]
P87C58X2@TTSOP38 [DX1049]
P87C591@TQFP44 [DX3002]
P87C652 [DX0001]
P87C652@TQFP44 [DX3002]
P87C654@PLCC44 [DX2044]
P87C660X2@PLCC44 [DX2044]
P87C661X2@PLCC44 [DX2044]
P87C748 [DX0001]
P87C749 [DX0001]
P87C750 [DX0001]
P87C750@SSOP24 [DX1026]
P87C751@PLCC28 [DX2028]
P87C752 [DX0001]
P87C752@SSOP28 [DX1026]
P87C754@PLCC28 [DX2028]
P87CL52X2 [DX0001]
P87CL52X2@TQFP44 [DX3005]
P87CL54X2 [DX0001]
P87CL54X2@TQFP44 [DX3005]
P87L51FA [DX0001]
P87L51FA@TQFP44 [DX3002]
P87L51FB@PLCC44 [DX2044]
P87LPC759 [DX0001]
P87LPC760 [DX0001]
P87LPC760@TSSOP14 [DX1000]
P87LPC761 [DX0001]

P87LPC761(ISP) [DX0001]
P87LPC762(ISP) [DX0001]
P87LPC762@PLCC44(ISP) [DX0001]
P87LPC762@SOIC20(ISP) [DX0001]
P87LPC764(ISP) [DX0001]
P87LPC764@PLCC44(ISP) [DX0001]
P87LPC764@SOIC20(ISP) [DX0001]
P87LPC764@TSSOP20(ISP) [DX0001]
P87LPC767(ISP) [DX0001]
P87LPC767@PLCC44(ISP) [DX0001]
P87LPC767@SOIC20(ISP) [DX0001]
P87LPC768(ISP) [DX0001]
P87LPC768@SOIC20(ISP) [DX0001]
P87LPC769(ISP) [DX0001]
P87LPC769@PLCC44(ISP) [DX0001]
P87LPC769@SOIC20(ISP) [DX0001]
P87LPC778(ISP) [DX0001]
P87LPC778@TSSOP20(ISP) [DX0001]
P87LPC779(ISP) [DX0001]
P87LPC779@TSSOP20(ISP) [DX0001]
P89C138@PLCC44 [DX2044]
P89C238 [DX0001]
P89C238@TQFP44 [DX3005]
P89C51B@PLCC44 [DX2044]
P89C51RA+ [DX0001]
P89C51RA+@TQFP44 [DX3005]
P89C51RA2B@PLCC44 [DX2044]
P89C51RB+ [DX0001]
P89C51RB+@TQFP44 [DX3005]
P89C51RB2B@PLCC44 [DX2044]
P89C51RB2H [DX0001]
P89C51RB2H@TQFP44 [DX3002]
P89C51RC+@PLCC44 [DX2044]
P89C51RC2B [DX0001]
P89C51RC2B@TQFP44 [DX3005]
P89C51RC2H@PLCC44 [DX2044]
P89C51RD+ [DX0001]
P89C51RD+@TQFP44 [DX3005]
P89C51RD2B@PLCC44 [DX2044]
P89C51RD2H [DX0001]
P89C51RD2H@TQFP44 [DX3002]
P89C51UB@PLCC44 [DX2044]
P89C51UF [DX0001]
P89C51UF@TQFP44 [DX3005]
P89C51X2@PLCC44 [DX2044]
P89C51X2B [DX0001]
P89C51X2B@TQFP44 [DX3005]
P89C51X2F@PLCC44 [DX2044]
P87LPC762 [DX0001]
P87LPC762@PLCC44 [DX1044]
P87LPC762@SOIC20 [DX1033]
P87LPC764 [DX0001]
P87LPC764@PLCC44 [DX1044]
P87LPC764@SOIC20 [DX1033]
P87LPC764@TSSOP20 [DX1001]
P87LPC767 [DX0001]
P87LPC767@PLCC44 [DX1044]
P87LPC767@SOIC20 [DX1033]
P87LPC768 [DX0001]
P87LPC768@SOIC20 [DX1033]
P87LPC769 [DX0001]
P87LPC769@PLCC44 [DX1044]
P87LPC769@SOIC20 [DX1033]
P87LPC778 [DX0001]
P87LPC778@TSSOP20 [DX1000]
P87LPC779 [DX0001]
P87LPC779@TSSOP20 [DX1000]
P89C138 [DX0001]
P89C138@TQFP44 [DX3005]
P89C238@PLCC44 [DX2044]
P89C51B [DX0001]
P89C51B@TQFP44 [DX3005]
P89C51RA+@PLCC44 [DX2044]
P89C51RA2B [DX0001]
P89C51RA2B@TQFP44 [DX3005]
P89C51RB+@PLCC44 [DX2044]
P89C51RB2B [DX0001]
P89C51RB2B@TQFP44 [DX3005]
P89C51RB2H@PLCC44 [DX2044]
P89C51RC+ [DX0001]
P89C51RC+@TQFP44 [DX3005]
P89C51RC2B@PLCC44 [DX2044]
P89C51RC2H [DX0001]
P89C51RC2H@TQFP44 [DX3002]
P89C51RD+@PLCC44 [DX2044]
P89C51RD2B [DX0001]
P89C51RD2B@TQFP44 [DX3005]
P89C51RD2H@PLCC44 [DX2044]
P89C51UB [DX0001]
P89C51UB@TQFP44 [DX3005]
P89C51UF@PLCC44 [DX2044]
P89C51X2 [DX0001]
P89C51X2@TQFP44 [DX3005]
P89C51X2B@PLCC44 [DX2044]
P89C51X2F [DX0001]
P89C51X2F@TQFP44 [DX3005]

P89C52 [DX0001]
P89C52@PLCC44 [DX2044]
P89C52@TQFP44 [DX3005]
P89C52B [DX0001]
P89C52B@PLCC44 [DX2044]
P89C52B@TQFP44 [DX3005]
P89C52UB [DX0001]
P89C52UB@PLCC44 [DX2044]
P89C52UB@TQFP44 [DX3005]
P89C52UF [DX0001]
P89C52UF@PLCC44 [DX2044]
P89C52UF@TQFP44 [DX3005]
P89C52X2 [DX0001]
P89C52X2@PLCC44 [DX2044]
P89C52X2@TQFP44 [DX3005]
P89C52X2B [DX0001]
P89C52X2B@PLCC44 [DX2044]
P89C52X2B@TQFP44 [DX3005]
P89C52X2F [DX0001]
P89C52X2F@PLCC44 [DX2044]
P89C52X2F@TQFP44 [DX3005]
P89C536@PLCC44 [DX2044]
P89C538@PLCC44 [DX2044]
P89C54 [DX0001]
P89C54@PLCC44 [DX2044]
P89C54@TQFP44 [DX3005]
P89C54B [DX0001]
P89C54B@PLCC44 [DX2044]
P89C54B@TQFP44 [DX3005]
P89C54UB [DX0001]
P89C54UB@PLCC44 [DX2044]
P89C54UB@TQFP44 [DX3005]
P89C54UF [DX0001]
P89C54UF@PLCC44 [DX2044]
P89C54UF@TQFP44 [DX3005]
P89C54X2 [DX0001]
P89C54X2@PLCC44 [DX2044]
P89C54X2@TQFP44 [DX3005]
P89C54X2B [DX0001]
P89C54X2B@PLCC44 [DX2044]
P89C54X2B@TQFP44 [DX3005]
P89C54X2F [DX0001]
P89C54X2F@PLCC44 [DX2044]
P89C54X2F@TQFP44 [DX3005]
P89C58 [DX0001]
P89C58@PLCC44 [DX2044]
P89C58@TQFP44 [DX3005]
P89C58B [DX0001]
P89C58B@PLCC44 [DX2044]
P89C58B@TQFP44 [DX3005]
P89C58UB [DX0001]
P89C58UB@PLCC44 [DX2044]
P89C58UB@TQFP44 [DX3005]
P89C58UF [DX0001]
P89C58UF@PLCC44 [DX2044]
P89C58UF@TQFP44 [DX3005]
P89C58X2 [DX0001]
P89C58X2@PLCC44 [DX2044]
P89C58X2@TQFP44 [DX3005]
P89C58X2B [DX0001]
P89C58X2B@PLCC44 [DX2044]
P89C58X2B@TQFP44 [DX3005]
P89C58X2F [DX0001]
P89C58X2F@PLCC44 [DX2044]
P89C58X2F@TQFP44 [DX3005]
P89C60X2 [DX0001]
P89C60X2@PLCC44 [DX2044]
P89C60X2@TQFP44 [DX3005]
P89C61X2 [DX0001]
P89C61X2@PLCC44 [DX2044]
P89C61X2@TQFP44 [DX3005]
P89C660 [DX0001]
P89C660@PLCC44 [DX2044]
P89C660@TQFP44 [DX3002]
P89C662 [DX0001]
P89C662@PLCC44 [DX2044]
P89C662@TQFP44 [DX3002]
P89C664 [DX0001]
P89C664@PLCC44 [DX2044]
P89C664@TQFP44 [DX3002]
P89C668 [DX0001]
P89C668@PLCC44 [DX2044]
P89C668@TQFP44 [DX3002]
P89C669 [DX0001]
P89C669@LQFP44 [DX3005]
P89C669@PLCC44 [DX2044]
P89C669X2 [DX0001]
P89C669X2@LQFP44 [DX3005]
P89C669X2@PLCC44 [DX2044]
P89C738 [DX0001]
P89C738@PLCC44 [DX2044]
P89C738@TQFP44 [DX3005]
P89C838 [DX0001]
P89C838@PLCC44 [DX2044]
P89C838@TQFP44 [DX3005]
P89CV51RB2@PLCC44 [DX2044]

P89CV51RB2@TQFP44 [DX3005]
P89CV51RC2@TQFP44 [DX3005]
P89CV51RD2@TQFP44 [DX3005]
P89LPC901(FD)(ISP) [DX0001]
P89LPC901(FN)(ISP) [DX0001]
P89LPC902(FD)(ISP) [DX0001]
P89LPC902(FN)(ISP) [DX0001]
P89LPC903(FD)(ISP) [DX0001]
P89LPC904(FD)(ISP) [DX0001]
P89LPC904(FN)(ISP) [DX0001]
P89LPC906(FD)(ISP) [DX0001]
P89LPC907(FD)(ISP) [DX0001]
P89LPC908(FD)(ISP) [DX0001]
P89LPC9103(FTK)@HVSON10 [DX4007]
P89LPC9107(FN) [DX3001]
P89LPC912(FDH)@TSSOP14(ISP) [DX0001]
P89LPC913(FDH)@TSSOP14 [DX1000]
P89LPC913(FDH)@TSSOP14(ISP) [DX0001]
P89LPC914(FDH)@TSSOP14 [DX1000]
P89LPC914(FDH)@TSSOP14(ISP) [DX0001]
P89LPC915(FDH)@TSSOP14 [DX1000]
P89LPC915(FDH)@TSSOP14(ISP) [DX0001]
P89LPC916(FDH)@TSSOP16 [DX1000]
P89LPC916(FDH)@TSSOP16(ISP) [DX0001]
P89LPC917(FDH)@TSSOP16 [DX1000]
P89LPC917(FDH)@TSSOP16(ISP) [DX0001]
P89LPC920(FDH)@TSSOP20 [DX1000]
P89LPC920(FDH)@TSSOP20(ISP) [DX0001]
P89LPC920(FN) [DX0001]
P89LPC9201(FDH)@TSSOP20 [DX1000]
P89LPC9201(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9201(FN) [DX0001]
P89LPC920A1(FDH)@TSSOP20 [DX1000]
P89LPC920A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC920A1(FN) [DX0001]
P89LPC921(FDH)@TSSOP20 [DX1000]
P89LPC921(FDH)@TSSOP20(ISP) [DX0001]
P89LPC921(FN) [DX0001]
P89LPC9211(FDH)@TSSOP20 [DX1000]
P89LPC9211(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9211(FN) [DX0001]
P89LPC921A1(FDH)@TSSOP20 [DX1000]
P89LPC921A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC921A1(FN) [DX0001]
P89LPC922(FDH)@TSSOP20 [DX1000]
P89LPC922(FDH)@TSSOP20(ISP) [DX0001]
P89LPC922(FN) [DX0001]
P89LPC9221(FDH)@TSSOP20 [DX1000]
P89LPC920(FN)(ISP) [DX0001]
P89LPC9201(FN)(ISP) [DX0001]
P89LPC920A1(FN)(ISP) [DX0001]
P89LPC921(FN)(ISP) [DX0001]
P89LPC9211(FN)(ISP) [DX0001]
P89LPC921A1(FN)(ISP) [DX0001]
P89LPC922(FN)(ISP) [DX0001]
P89CV51RC2@PLCC44 [DX2044]
P89CV51RD2@PLCC44 [DX2044]
P89LPC901(FD) [DX1045]
P89LPC901(FN) [DX0001]
P89LPC902(FD) [DX1045]
P89LPC902(FN) [DX0001]
P89LPC903(FD) [DX1045]
P89LPC904(FD) [DX1045]
P89LPC904(FN) [DX1045]
P89LPC906(FD) [DX1045]
P89LPC907(FD) [DX1045]
P89LPC908(FD) [DX1045]
P89LPC9102(FTK)@HVSON10 [DX4007]
P89LPC9107(FDH)@TSSOP14 [DX1001]
P89LPC912(FDH)@TSSOP14 [DX1000]

P89LPC9221(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9221(FN) [DX0001]
P89LPC9221(FN)(ISP) [DX0001]
P89LPC9221A1(FDH)@TSSOP20 [DX1000]
P89LPC9221A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9221A1(FN) [DX0001]
P89LPC9221A1(FN)(ISP) [DX0001]
P89LPC922A1(FDH)@TSSOP20 [DX1000]
P89LPC922A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC922A1(FN) [DX0001]
P89LPC922A1(FN)(ISP) [DX0001]
P89LPC924(FDH)@TSSOP20 [DX1000]
P89LPC924(FDH)@TSSOP20(ISP) [DX0001]
P89LPC924(FN) [DX0001]
P89LPC924(FN)(ISP) [DX0001]
P89LPC9241(FDH)@TSSOP20 [DX1000]
P89LPC9241(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9241(FN) [DX0001]
P89LPC9241(FN)(ISP) [DX0001]
P89LPC924A1(FDH)@TSSOP20 [DX1000]
P89LPC924A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC924A1(FN) [DX0001]
P89LPC924A1(FN)(ISP) [DX0001]
P89LPC925(FDH)@TSSOP20 [DX1000]
P89LPC925(FDH)@TSSOP20(ISP) [DX0001]
P89LPC925(FN) [DX0001]
P89LPC925(FN)(ISP) [DX0001]
P89LPC9251(FDH)@TSSOP20 [DX1000]
P89LPC9251(FDH)@TSSOP20(ISP) [DX0001]
P89LPC9251(FN) [DX0001]
P89LPC9251(FN)(ISP) [DX0001]
P89LPC925A1(FDH)@TSSOP20 [DX1000]
P89LPC925A1(FDH)@TSSOP20(ISP) [DX0001]
P89LPC925A1(FN) [DX0001]
P89LPC925A1(FN)(ISP) [DX0001]
P89LPC930(BA)@PLCC28 [DX2028]
P89LPC930(BA)@PLCC28(ISP) [DX0001]
P89LPC930(BDH)@TSSOP28 [DX1001]
P89LPC930(BDH)@TSSOP28(ISP) [DX0001]
P89LPC9301(BA)@PLCC28 [DX2028]
P89LPC9301(BDH)@TSSOP28 [DX1001]
P89LPC9301FA [DX2028]
P89LPC9301FDH [DX1001]
P89LPC930FA [DX2028]
P89LPC930FDH [DX1001]
P89LPC931(BA)@PLCC28 [DX2028]
P89LPC931(BA)@PLCC28(ISP) [DX0001]
P89LPC931(BDH)@TSSOP28 [DX1001]
P89LPC931(BDH)@TSSOP28(ISP) [DX0001]
P89LPC9311(BA)@PLCC28 [DX2028]
P89LPC9311(BDH)@TSSOP28 [DX1001]
P89LPC9311FA [DX2028]
P89LPC9311FDH [DX1001]
P89LPC931FA [DX2028]
P89LPC931FDH [DX1001]
P89LPC932(BA)@PLCC28 [DX2028]
P89LPC932(BDH)@TSSOP28 [DX1001]
P89LPC932(FA)@PLCC28 [DX2028]
P89LPC93201BA@PLCC28 [DX2028]
P89LPC93201BDH@TSSOP28 [DX1001]
P89LPC93201FA@PLCC28 [DX2028]
P89LPC93201FDH@TSSOP28 [DX1001]
P89LPC93201FHN@QFN28 [DX4014]
P89LPC9321BA@PLCC28 [DX2028]
P89LPC9321BDH@TSSOP28 [DX1001]
P89LPC9321FA@PLCC28 [DX2028]
P89LPC9321FDH@TSSOP28 [DX1001]
P89LPC9321FHN@QFN28 [DX4014]
P89LPC932A1(BA)@PLCC28 [DX2028]
P89LPC932A1(BA)@PLCC28(ISP) [DX0001]

P89LPC932A1(BDH)@TSSOP28 [DX1001]
P89LPC932A1(BDH)@TSSOP28(ISP) [DX0001]
P89LPC932A1(FA)@PLCC28 [DX2028]
P89LPC932A1(FDH)@TSSOP28 [DX1001]
P89LPC932A1(FDH)@TSSOP28(ISP) [DX0001]
P89LPC932A1(FHN)@HVQFN28 [DX4014]
P89LPC932A1(FHN)@HVQFN28(ISP) [DX0001]
P89LPC933(BDH)@TSSOP28 [DX1001]
P89LPC933(BDH)@TSSOP28(ISP) [DX0001]
P89LPC933(FDH)@TSSOP28 [DX1001]
P89LPC933(FDH)@TSSOP28(ISP) [DX0001]
P89LPC933(HDH)@TSSOP28 [DX1001]　　P89LPC9331(BDH)@TSSOP28 [DX1001]
P89LPC9331(FDH)@TSSOP28 [DX1001]　　P89LPC9331(HDH)@TSSOP28 [DX1001]
P89LPC934(BDH)@TSSOP28 [DX1001]
P89LPC934(BDH)@TSSOP28(ISP) [DX0001]
P89LPC934(FDH)@TSSOP28 [DX1001]
P89LPC934(FDH)@TSSOP28(ISP) [DX0001]
P89LPC93401(FDH)@TSSOP28 [DX1001]
P89LPC93401V [DX0001]　　P89LPC9341(BDH)@TSSOP28 [DX1001]
P89LPC9341(FDH)@TSSOP28 [DX1001]　　P89LPC9341V [DX0001]
P89LPC935(BA)@PLCC28 [DX2028]
P89LPC935(BA)@PLCC28(ISP) [DX0001]
P89LPC935(BDH)@TSSOP28 [DX1001]
P89LPC935(BDH)@TSSOP28(ISP) [DX0001]
P89LPC935(FA)@PLCC28 [DX2028]
P89LPC935(FA)@PLCC28(ISP) [DX0001]
P89LPC935(FDH)@TSSOP28 [DX1001]
P89LPC935(FDH)@TSSOP28(ISP) [DX0001]
P89LPC935(FHN)@HVQFN28 [DX4014]
P89LPC935(FHN)@HVQFN28(ISP) [DX0001]
P89LPC93501BA@PLCC28 [DX2028]　　P89LPC93501BDH@TSSOP28 [DX1001]
P89LPC93501FA@PLCC28 [DX2028]　　P89LPC93501FDH@TSSOP28 [DX1001]
P89LPC93501FHN@QFN28 [DX4014]　　P89LPC9351BA@PLCC28 [DX2028]
P89LPC9351BDH@TSSOP28 [DX1001]　　P89LPC9351FA@PLCC28 [DX2028]
P89LPC9351FDH@TSSOP28 [DX1001]　　P89LPC9351FHN@QFN28 [DX4014]
P89LPC936(FA)@PLCC28 [DX2028]　　P89LPC936(FDH)@TSSOP28 [DX1001]
P89LPC9361(FA)@PLCC28 [DX2028]　　P89LPC9361(FDH)@TSSOP28 [DX1001]
P89LPC938(FA)@PLCC28 [DX2028]
P89LPC938(FA)@PLCC28(ISP) [DX0001]
P89LPC938(FDH)@TSSOP28 [DX1001]
P89LPC938(FDH)@TSSOP28(ISP) [DX0001]
P89LPC938(FHN)@HVQFN28 [DX4014]
P89LPC938(FHN)@HVQFN28(ISP) [DX0001]
P89LPC93801BA@PLCC28 [DX2028]　　P89LPC93801BDH@TSSOP28 [DX1001]
P89LPC93801FA@PLCC28 [DX2028]　　P89LPC93801FDH@TSSOP28 [DX1001]
P89LPC93801FHN@QFN28 [DX4014]　　P89LPC9381BA@PLCC28 [DX2028]
P89LPC9381BDH@TSSOP28 [DX1001]　　P89LPC9381FA@PLCC28 [DX2028]
P89LPC9381FDH@TSSOP28 [DX1001]　　P89LPC9381FHN@QFN28 [DX4014]

P89LPC9401(FBD)@LQFP64 [DX3013]
P89LPC9401(FBD)@LQFP64(ISP) [DX0001]
P89LPC9402(FBD)@LQFP64 [DX3013]
P89LPC9408(FBD)@LQFP64 [DX3013]
P89LPC9408(FBD)@LQFP64(ISP) [DX0001]
P89LPC952@LQFP44 [DX3005]
P89LPC952@LQFP44(ISP) [DX0001]
P89LPC952@LQFP48 [DX3007]
P89LPC952@LQFP48(ISP) [DX0001]
P89LPC952@PLCC44 [DX2044]
P89LPC952@PLCC44(ISP) [DX0001]
P89LPC954@LQFP44 [DX3005]
P89LPC954@LQFP44(ISP) [DX0001]
P89LPC954@LQFP48 [DX3007]
P89LPC954@LQFP48(ISP) [DX0001]
P89LPC954@PLCC44 [DX2044]
P89LPC954@PLCC44(ISP) [DX0001]
P89LPC970FDH@TSSOP20 [DX1000]
P89LPC970FDH@TSSOP20(serial) [DX1000]
P89LPC970FN [DX0001]
P89LPC970FN(serial) [DX0001]
P89LPC971FDH@TSSOP20 [DX1000]
P89LPC971FDH@TSSOP20(serial) [DX1000]
P89LPC971FN [DX0001]
P89LPC971FN(serial) [DX0001]
P89LPC972FDH@TSSOP20 [DX1000]
P89LPC972FDH@TSSOP20(serial) [DX1000]
P89LPC972FN [DX0001]
P89LPC972FN(serial) [DX0001]
P89LPC980FDH@TSSOP28 [DX1001]
P89LPC980FDH@TSSOP28(serial) [DX1001]
P89LPC982FDH@TSSOP28 [DX1001]
P89LPC982FDH@TSSOP28(serial) [DX1001]
P89LPC983FA@PLCC28 [DX2028]
P89LPC983FA@PLCC28(serial) [DX2028]
P89LPC983FDH@TSSOP28 [DX1001]
P89LPC983FDH@TSSOP28(serial) [DX1001]
P89LPC985FA@PLCC28 [DX2028]
P89LPC985FA@PLCC28(serial) [DX2028]
P89LPC985FDH@TSSOP28 [DX1001]
P89LPC985FDH@TSSOP28(serial) [DX1001]
P89LPC9902FTK [DX4047]
P89LPC9903FTK [DX4047]
P89LV51RB2 [DX0001]
P89LV51RB2@PLCC44 [DX2044]
P89LV51RB2@TQFP44 [DX3005]
P89LV51RB2FA@PLCC44 [DX2044]
P89LV51RB2FBC@TQFP44 [DX3005]
P89LV51RB2FN [DX0001]
P89LV51RC2 [DX0001]
P89LV51RC2@PLCC44 [DX2044]
P89LV51RC2@TQFP44 [DX3005]
P89LV51RC2FA@PLCC44 [DX2044]
P89LV51RC2FBC@TQFP44 [DX3005]
P89LV51RC2FN [DX0001]
P89LV51RD2 [DX0001]
P89LV51RD2(new) [DX0001]
P89LV51RD2(new)@PLCC44 [DX2044]
P89LV51RD2(new)@TQFP44 [DX3005]
P89LV51RD2@PLCC44 [DX2044]
P89LV51RD2@TQFP44 [DX3005]
P89LV51RD2BA(new)@PLCC44 [DX2044]
P89LV51RD2BA@PLCC44 [DX2044]
P89LV51RD2BBC(new)@TQFP44 [DX3005]
P89LV51RD2BBC@TQFP44 [DX3005]
P89LV51RD2BN [DX0001]
P89LV51RD2BN(new) [DX0001]
P89LV51RD2FA(new)@PLCC44 [DX2044]
P89LV51RD2FA@PLCC44 [DX2044]

P89LV51RD2FBC(new)@TQFP44 [DX3005]
P89LV51RD2FBC@TQFP44 [DX3005]
P89LV51RD2FN [DX0001]
P89LV51RD2FN(new) [DX0001]
P89V51RB2 [DX0001]
P89V51RB2@PLCC44 [DX2044]
P89V51RB2@TQFP44 [DX3005]
P89V51RB2FA@PLCC44 [DX2044]
P89V51RB2FBC@TQFP44 [DX3005]
P89V51RB2FN [DX0001]
P89V51RC2 [DX0001]
P89V51RC2@PLCC44 [DX2044]
P89V51RC2@TQFP44 [DX3005]
P89V51RC2FA@PLCC44 [DX2044]
P89V51RC2FBC@TQFP44 [DX3005]
P89V51RC2FN [DX0001]
P89V51RD2 [DX0001]
P89V51RD2(new) [DX0001]
P89V51RD2(new)@PLCC44 [DX2044]
P89V51RD2(new)@TQFP44 [DX3005]
P89V51RD2@PLCC44 [DX2044]
P89V51RD2@TQFP44 [DX3005]
P89V51RD2BA(new)@PLCC44 [DX2044]
P89V51RD2BA@PLCC44 [DX2044]
P89V51RD2BBC(new)@TQFP44 [DX3005]
P89V51RD2BBC@TQFP44 [DX3005]
P89V51RD2BN [DX0001]
P89V51RD2BN(new) [DX0001]
P89V51RD2FA(new)@PLCC44 [DX2044]
P89V51RD2FA@PLCC44 [DX2044]
P89V51RD2FBC(new)@TQFP44 [DX3005]
P89V51RD2FBC@TQFP44 [DX3005]
P89V51RD2FN [DX0001]
P89V51RD2FN(new) [DX0001]
P89V52X2 [DX0001]
P89V52X2(ISP) [DX0001]
P89V52X2@PLCC44 [DX2044]
P89V52X2@PLCC44(ISP) [DX0001]
P89V52X2@TQFP44 [DX3005]
P89V52X2@TQFP44(ISP) [DX0001]
P89V54X2 [DX0001]
P89V54X2(ISP) [DX0001]
P89V54X2@PLCC44 [DX2044]
P89V54X2@PLCC44(ISP) [DX0001]
P89V54X2@TQFP44 [DX3005]
P89V54X2@TQFP44(ISP) [DX0001]
P89V660@PLCC44 [DX2044]
P89V660@TQFP44 [DX3005]
P89V662@PLCC44 [DX2044]
P89V662@TQFP44 [DX3005]
P89V664@PLCC44 [DX2044]
P89V664@TQFP44 [DX3005]
PCF7931 [DX1026]
PCF7931ATS [DX1026]
PCF7931ATSM1AB [DX1026]
PCF7931ATSM2AB [DX1026]
PCF7931ATT [DX1001]
PCF7931ATTM1AB [DX1001]
PCF7931ATTM2AB [DX1001]
PCF7931M1AB [DX1026]
PCF7931M2AB [DX1026]
PCF7941 [DX1026]
PCF7941ATS [DX1026]
PCF7941ATSM1AB [DX1026]
PCF7941ATSM2AB [DX1026]
PCF7941ATT [DX1001]
PCF7941ATTM1AB [DX1001]
PCF7941ATTM2AB [DX1001]
PCF7941M1AB [DX1026]
PCF7941M2AB [DX1026]
PCF7945 [DX1001]
PCF7952@TSSOP24 [DX1001]
PCF7952AC1500 [DX1000]
PCF7952ATT [DX1000]
PCF7961ATTM1AB [DX1001]
PCF7961ATTM1AC [DX1001]
PCF7961ATTM1AE [DX1001]
PCH7971 [DX1081]
PSD301@PLCC44 [DX2044]
PSD301L@PLCC44 [DX2044]
PSD302@PLCC44 [DX2044]
PSD302L@PLCC44 [DX2044]
PSD303@PLCC44 [DX2044]
PSD303L@PLCC44 [DX2044]
PSD311@PLCC44 [DX2044]
PSD311L@PLCC44 [DX2044]
PSD312@PLCC44 [DX2044]
PSD312L@PLCC44 [DX2044]
PSD313@PLCC44 [DX2044]
PSD313@TQFP44 [DX3003]
PSD313-B@PLCC44 [DX2044]

PSD313-B@TQFP44 [DX3003]
PSD313L@TQFP44 [DX3003]
PXAC37@TQFP44 [DX3003]
PXAG17@TQFP44 [DX3003]
PXAG27@TQFP44 [DX3003]
PXAG37@TQFP44 [DX3003]
PXAG39@TQFP44 [DX3003]
PXAG39K@TQFP44 [DX3003]
PXAG49@TQFP44 [DX3003]
PXAG49K@TQFP44 [DX3003]
PXAS37@PQFP80 [DX3016]
SP37 [DX1081]
SP373 [DX1081]
TDA11105H1@PQFP80 [DX3019]
TDA11106H@PQFP80 [DX3019]
TDA11106PS@SDIP64 [DX0064]
TDA11112H1@PQFP80 [DX3019]
TDA11115H@PQFP80 [DX3019]
TDA11115PS@SDIP64 [DX0064]
TDA11116H1@PQFP80 [DX3019]
TDA11125H@PQFP80 [DX3019]
TDA11125PS@SDIP64 [DX0064]
TDA11126H1@PQFP80 [DX3019]
TDA11135H@PQFP80 [DX3019]
TDA11135PS@SDIP64 [DX0064]
TDA11136H1@PQFP80 [DX3019]
TDA11142H@PQFP80 [DX3019]
TDA11142PS@SDIP64 [DX0064]
TDA11145H1@PQFP80 [DX3019]
TDA11146H@PQFP80 [DX3019]
TDA11146PS@SDIP64 [DX0064]
TDA11155H1@PQFP80 [DX3019]
TDA11156H@PQFP80 [DX3019]
TDA11156PS@SDIP64 [DX0064]
TDA12100H1@PQFP80 [DX3019]
TDA12110H1@PQFP80 [DX3019]
TDA12120H1@PQFP80 [DX3019]
TDA12135H1@PQFP80 [DX3019]
TDA12136H@PQFP80 [DX3019]
TDA12136PS@SDIP64 [DX0064]
TDA12140H1@PQFP80 [DX3019]
TDA12155H1@PQFP80 [DX3019]
TDA12156H@PQFP80 [DX3019]
TDA12156PS@SDIP64 [DX0064]
TDA12165H1@PQFP80 [DX3019]
TDA12166H@PQFP80 [DX3019]
TDA12166PS@SDIP64 [DX0064]
TDA12175H1@PQFP80 [DX3019]
PSD313L@PLCC44 [DX2044]
PXAC37@PLCC44 [DX2044]
PXAG17@PLCC44 [DX2044]
PXAG27@PLCC44 [DX2044]
PXAG37@PLCC44 [DX2044]
PXAG39@PLCC44 [DX2044]
PXAG39K@PLCC44 [DX2044]
PXAG49@PLCC44 [DX2044]
PXAG49K@PLCC44 [DX2044]
PXAS37@PLCC68 [DX2068]
SP30 [DX1081]
SP370 [DX1081]
TDA11105H@PQFP80 [DX3019]
TDA11105PS@SDIP64 [DX0064]
TDA11106H1@PQFP80 [DX3019]
TDA11112H@PQFP80 [DX3019]
TDA11112PS@SDIP64 [DX0064]
TDA11115H1@PQFP80 [DX3019]
TDA11116H@PQFP80 [DX3019]
TDA11116PS@SDIP64 [DX0064]
TDA11125H1@PQFP80 [DX3019]
TDA11126H@PQFP80 [DX3019]
TDA11126PS@SDIP64 [DX0064]
TDA11135H1@PQFP80 [DX3019]
TDA11136H@PQFP80 [DX3019]
TDA11136PS@SDIP64 [DX0064]
TDA11142H1@PQFP80 [DX3019]
TDA11145H@PQFP80 [DX3019]
TDA11145PS@SDIP64 [DX0064]
TDA11146H1@PQFP80 [DX3019]
TDA11155H@PQFP80 [DX3019]
TDA11155PS@SDIP64 [DX0064]
TDA11156H1@PQFP80 [DX3019]
TDA12100H@PQFP80 [DX3019]
TDA12110H@PQFP80 [DX3019]
TDA12120H@PQFP80 [DX3019]
TDA12135H@PQFP80 [DX3019]
TDA12135PS@SDIP64 [DX0064]
TDA12136H1@PQFP80 [DX3019]
TDA12140H@PQFP80 [DX3019]
TDA12155H@PQFP80 [DX3019]
TDA12155PS@SDIP64 [DX0064]
TDA12156H1@PQFP80 [DX3019]
TDA12165H@PQFP80 [DX3019]
TDA12165PS@SDIP64 [DX0064]
TDA12166H1@PQFP80 [DX3019]
TDA12175H@PQFP80 [DX3019]
TDA12175PS@SDIP64 [DX0064]

TDA12176H@PQFP80 [DX3019]
TDA12176H1@PQFP80 [DX3019]
TDA12176PS@SDIP64 [DX0064]
TDA12185H@PQFP80 [DX3019]
TDA12185H1@PQFP80 [DX3019]
TDA12185PS@SDIP64 [DX0064]
TDA12186H@PQFP80 [DX3019]
TDA12186H1@PQFP80 [DX3019]
TDA12186PS@SDIP64 [DX0064]
TDA12195H@PQFP80 [DX3019]
TDA12195H1@PQFP80 [DX3019]
TDA12195PS@SDIP64 [DX0064]
TDA12196H@PQFP80 [DX3019]
TDA12196H1@PQFP80 [DX3019]
TDA12196PS@SDIP64 [DX0064]
UOCIIIN1A-128K@QIP90 [DX0090]
UOCIIIN1A-128K@QIP90(facedown) [DX0090]
UOCIIIN1A-128K@TQFP128 [DX3033]
UOCIIIN1A-128K@TQFP128(facedown) [DX3033]
UOCIIIN1A-256K@QIP90 [DX0090]
UOCIIIN1A-256K@QIP90(facedown) [DX0090]
UOCIIIN1A-256K@TQFP128 [DX3033]
UOCIIIN1A-256K@TQFP128(facedown) [DX3033]
UOCIIIN1B-128K@QIP90 [DX0090]
UOCIIIN1B-128K@QIP90(facedown) [DX0090]
UOCIIIN1B-128K@TQFP128 [DX3033]
UOCIIIN1B-128K@TQFP128(facedown) [DX3033]
UOCIIIN1B-256K@QIP90 [DX0090]
UOCIIIN1B-256K@QIP90(facedown) [DX0090]
UOCIIIN1B-256K@TQFP128 [DX3033]
UOCIIIN1B-256K@TQFP128(facedown) [DX3033]
UOCIIIN1D-128K@QIP90 [DX0090]
UOCIIIN1D-128K@QIP90(facedown) [DX0090]
UOCIIIN1D-128K@TQFP128 [DX3033]
UOCIIIN1D-128K@TQFP128(facedown) [DX3033]
UOCIIIN1D-256K@QIP90 [DX0090]
UOCIIIN1D-256K@QIP90(facedown) [DX0090]
UOCIIIN1D-256K@TQFP128 [DX3033]
UOCIIIN1D-256K@TQFP128(facedown) [DX3033]
UOCIIIN1E-128K@QIP90 [DX0090]
UOCIIIN1E-128K@QIP90(facedown) [DX0090]
UOCIIIN1E-128K@TQFP128 [DX3033]
UOCIIIN1E-128K@TQFP128(facedown) [DX3033]
UOCIIIN1E-256K@QIP90 [DX0090]
UOCIIIN1E-256K@QIP90(facedown) [DX0090]
UOCIIIN1E-256K@TQFP128 [DX3033]
UOCIIIN1E-256K@TQFP128(facedown) [DX3033]
UOCIIIN1F-128K@QIP90 [DX0090]
UOCIIIN1F-128K@QIP90(facedown) [DX0090]
UOCIIIN1F-128K@TQFP128 [DX3033]
UOCIIIN1F-128K@TQFP128(facedown) [DX3033]
UOCIIIN1F-256K@QIP90 [DX0090]
UOCIIIN1F-256K@QIP90(facedown) [DX0090]
UOCIIIN1F-256K@TQFP128 [DX3033]
UOCIIIN1F-256K@TQFP128(facedown) [DX3033]

PJ

E(E)PROM/FRAM/NVRAM

PJ24C02 [DX0001]
PJ24C02@SOIC8 [DX1045]
PJ24C02@TSSOP8 [DX1059]

PMC

E(E)PROM/FRAM/NVRAM

PM24C64 [DX0001]
PM24C64@SOIC8 [DX1045]
PM24C64@TSOP8 [DX1059]
PM25LD512(B)@SOIC8 [DX1044]
PM25LD512(Q)@WSON8 [DX4005]
PM25LD512(S)@SOIC8 [DX1045]
PM25LQ010B@SOIC8 [DX1045]
PM25LQ010B@TSSOP8 [DX1045]
PM25LQ032@SOIC8 [DX1044#1]
PM25LQ032@WSON8 [DX4006#1]
PM25LQ040(B)@SOIC8 [DX1044#1]
PM25LQ040(Q)@WSON8 [DX4005#1]
PM25LQ040(S)@SOIC8 [DX1045#1]
PM25LQ512B@SOIC8 [DX1045]
PM25LQ512B@TSSOP8 [DX1000]
PM25LV010(B)@SOIC8 [DX1044]
PM25LV010(Q)@WSON8 [DX4005]
PM25LV010(S)@SOIC8 [DX1045]
PM25LV010A(B)@SOIC8 [DX1044]
PM25LV010A(Q)@WSON8 [DX4005]
PM25LV010A(S)@SOIC8 [DX1045]
PM25LV020(B)@SOIC8 [DX1044#1]
PM25LV020(Q)@WSON8 [DX4005#1]
PM25LV020(S)@SOIC8 [DX1045#1]
PM25LV040(B)@SOIC8 [DX1044#1]
PM25LV040(Q)@WSON8 [DX4005#1]
PM25LV040(S)@SOIC8 [DX1045#1]
PM25LV512(B)@SOIC8 [DX1044]
PM25LV512(Q)@WSON8 [DX4005]
PM25LV512(S)@SOIC8 [DX1045]
PM25LV512A(B)@SOIC8 [DX1044]
PM25LV512A(Q)@WSON8 [DX4005]
PM25LV512A(S)@SOIC8 [DX1045]
PM25LV512A@TSSOP8 [DX1059]
PM29F002B [DX0001]
PM29F002B@PLCC32 [DX2032]
PM29F002T [DX0001]
PM29F002T@PLCC32 [DX2032]
PM29F004B [DX0001]
PM29F004B@PLCC32 [DX2032]
PM29F004T [DX0001]
PM29F004T@PLCC32 [DX2032]
PM29LV002B [DX0001]
PM29LV002B@PLCC32 [DX2032]
PM29LV002B@VSOP32 [DX1003]
PM29LV002T [DX0001]
PM29LV002T@PLCC32 [DX2032]
PM29LV002T@VSOP32 [DX1003]
PM29LV004B@PLCC32 [DX2032]
PM29LV004B@VSOP32 [DX1003]
PM29LV004T@PLCC32 [DX2032]
PM29LV004T@VSOP32 [DX1003]
PM29LV104RB@PLCC32 [DX2032]
PM29LV104RB@VSOP32 [DX1003]
PM29LV104RT@PLCC32 [DX2032]
PM29LV104RT@VSOP32 [DX1003]
PM37LV512 [DX0001]
PM37LV512@PLCC32 [DX2032]
PM37LV512@VSOP32 [DX1003]
PM39F010 [DX0001]
PM39F010@PLCC32 [DX2032]
PM39F010@VSOP32 [DX1003]
PM39F020 [DX0001]
PM39F020@PLCC32 [DX2032]
PM39F020@VSOP32 [DX1003]
PM39F040 [DX0001]
PM39F040@PLCC32 [DX2032]
PM39F040@VSOP32 [DX1003]
PM39LV010@PLCC32 [DX2032]
PM39LV010@VSOP32 [DX1003]

PM39LV010R@PLCC32 [DX2032]
PM39LV020@PLCC32 [DX2032]
PM39LV040@PLCC32 [DX2032]
PM39LV512@PLCC32 [DX2032]
PM39LV512R@PLCC32 [DX2032]
PM49FL002T@PLCC32 [DX2032]
PM49FL004T@PLCC32 [DX2032]
PM49FL008T@PLCC32 [DX2032]
PM49LP002T@PLCC32 [DX2032]
PM39LV010R@VSOP32 [DX1003]
PM39LV020@VSOP32 [DX1003]
PM39LV040@VSOP32 [DX1003]
PM39LV512@VSOP32 [DX1003]
PM39LV512R@VSOP32 [DX1003]
PM49FL002T@VSOP32 [DX1003]
PM49FL004T@VSOP32 [DX1003]
PM49FL008T@VSOP32 [DX1003]
PM49LP002T@VSOP32 [DX1003]

PORTEK

E(E)PROM/FRAM/NVRAM

PTK24A02T [DX0001]
PTK24A04T [DX0001]
PTK24A08T [DX0001]
PTK24A16T [DX0001]
PTK24A02T@SOIC8 [DX1045]
PTK24A04T@SOIC8 [DX1045]
PTK24A08T@SOIC8 [DX1045]
PTK24A16T@SOIC8 [DX1045]

POWERFLASH

E(E)PROM/FRAM/NVRAM

ASU1GA30HT@TSOP48 [DX1004-3]

POWER-RAIL

MICROCONTROLLER

MP01002 [DX0001]
MP01004 [DX0001]
MP01006 [DX0001]
MP01006XQN32 [DX4039-5]
MP01006XQP48 [DX3007-5]
MP01006XQP64 [DX3011-5]
MP01008 [DX0001]
MP01008XLQ48 [DX3007]
MP01008XLQ64 [DX3011]
MP01008XLQ80 [DX3060]
MP01010 [DX0001]
MP3004@LQFP48 [DX0001]
MP3004@LQFP64 [DX0001]
MP3004@QFP32 [DX0001]
MP3004@QFP64 [DX0001]
MP3004@SSOP28 [DX0001]
MP4132XLQ64 [DX3011]
MP6016X [DX0001]
MP6116X [DX0001]
MP6116XQN32 [DX4039-5]
MP6116XQP48 [DX3007-5]
MP6116XQP64 [DX3011-5]
MP8132XLQ48 [DX3007]
MP8132XLQ64 [DX3011]
MP8132XLQ80 [DX3060]

PSS

E(E)PROM/FRAM/NVRAM

PS24C256 [DX0001]
PS24C256@SOIC8 [DX1045]

PTC

E(E)PROM/FRAM/NVRAM

PT28C020 [DX0001]
PT28C020@PLCC32 [DX2032]
PT28C040 [DX0001]
PT28C040@PLCC32 [DX2032]
PT29C020 [DX0001]
PT29C020@PLCC32 [DX2032]
PT29C040 [DX0001]
PT29C040@PLCC32 [DX2032]

MICROCONTROLLER

PT8936 [DX0001]
PT8936@PLCC44 [DX2044]
PT8936@TQFP44 [DX3002]
PT8956 [DX0001]
PT8956@PLCC44 [DX2044]
PT8956@TQFP44 [DX3002]

QISDA-CUSTOMER

E(E)PROM/FRAM/NVRAM

AT24C32C [DX0001]
BR24S32 [DX0001]
RM24C32C [DX0001]

QIXIN

MICROCONTROLLER

LS2051 [DX0001]
LS2051@SOIC20 [DX1031]
LS4051 [DX0001]
LS4051@SOIC20 [DX1031]

QP semiconductor

E(E)PROM/FRAM/NVRAM

QP7C271 [DX0001]
QP7C271@PLCC32 [DX2032]

Quick Pulse

E(E)PROM/FRAM/NVRAM

27010 [DX0001]
27011 [DX0001]
27040 [DX0001]
27128A [DX0001]
27210 [DX0001]
27256 [DX0001]
27512 [DX0001]
2764A [DX0001]

RAMTRON

E(E)PROM/FRAM/NVRAM

FM1208 [DX0001]
FM1208@SOIC24 [DX1033]
FM1608 [DX0001]
FM1608@SOIC28 [DX1033]
FM1608B [DX0001]
FM1608B@SOIC28 [DX1033]
FM16W08 [DX0001]
FM16W08@SOIC28 [DX1033]
FM1808 [DX0001]
FM1808@SOIC28 [DX1033]
FM1808B [DX0001]
FM1808B@SOIC28 [DX1033]
FM18L08 [DX0001]
FM18L08@SOIC28 [DX1033]
FM18W08 [DX0001]
FM18W08@SOIC28 [DX1033]
FM20L08@TSOP32 [DX1053]
FM21L16@TSOP44 [DX1046]
FM21LD16@FBGA48 [DX5085]
FM22L16@TSOP44 [DX1046]
FM22LD16@FBGA48 [DX5085]
FM23MLD16@FBGA48 [DX5002]
FM24164 [DX0001]
FM24164@SOIC8 [DX1045]
FM24C04(P) [DX0001]
FM24C04(S)@SOP8 [DX1045]
FM24C04A(P) [DX0001]
FM24C04A(S)@SOP8 [DX1045]
FM24C04B@SOIC8 [DX1045]
FM24C04C@SOIC8 [DX1045]
FM24C08A [DX0001]
FM24C08A@SOP8 [DX1045]
FM24C16(P) [DX0001]
FM24C16(S)@SOP8 [DX1045]
FM24C16A(P) [DX0001]
FM24C16A(S)@SOP8 [DX1045]
FM24C16B@SOIC8 [DX1045]
FM24C16C@SOIC8 [DX1045]
FM24C256@SOIC8 [DX1045]
FM24C512@SOIC8 [DX1044]
FM24C64 [DX0001]
FM24C64@SOIC8 [DX1045]
FM24C64B@SOIC8 [DX1045]
FM24C64C@SOIC8 [DX1045]
FM24CL04 [DX0001]
FM24CL04@SOIC8 [DX1045]
FM24CL04B@SOIC8 [DX1045]
FM24CL16 [DX0001]
FM24CL16@SOIC8 [DX1045]
FM24CL16B@SOIC8 [DX1045]
FM24CL16B@TDFN8 [DX0001]
FM24CL64@SOIC8 [DX1045]
FM24CL64B@SOIC8 [DX1045]
FM24CL64B-GA@SOIC8 [DX1045]
FM24V01@SOIC8 [DX1045]
FM24V02@SOIC8 [DX1045]
FM24V05@SOIC8 [DX1044]
FM24V10@SOIC8 [DX1045]
FM24VN01@SOIC8 [DX1045]
FM24VN02@SOIC8 [DX1045]
FM24W256@SOIC8(150mil) [DX1045]
FM24W256@SOIC8(200mil) [DX1044]
FM25040 [DX0001]
FM25040@SOIC8 [DX1045]
FM25040B@SOIC8 [DX1045]
FM25160 [DX0001]
FM25160@SOIC8 [DX1045]
FM25640 [DX0001]
FM25640@SOIC8 [DX1016]
FM25640B [DX0001]
FM25640B@SOIC8 [DX1016]
FM25C160 [DX0001]
FM25C160@SOIC8 [DX1045]
FM25CL04@SOIC8 [DX1045]
FM25CL64 [DX0001]
FM25CL64@SOIC8 [DX1045]

FM25CL64B@SOIC8 [DX1045]
FM25CL64B@TDFN8 [DX4005]
FM25E64@SOIC8 [DX1045]
FM25H20@SOIC8 [DX1045#1]
FM25H20@TDFN8 [DX0001]
FM25L04B@SOIC8 [DX1045]
FM25L16 [DX0001]
FM25L16@SOIC8 [DX1045]
FM25L256 [DX0001]
FM25L256@SOIC8 [DX1045#1]
FM25L256@TDFN8 [DX0001]
FM25L256B [DX0001]
FM25L256B@SOIC8 [DX1045#1]
FM25L256B@TDFN8 [DX0001]
FM25L512 [DX0001]
FM25L512@SOIC8 [DX1045#1]
FM25LX64@SOIC8 [DX1045]
FM25P16@SOIC8 [DX1045]
FM25V01@SOIC8 [DX1045#1]
FM25V02@SOIC8 [DX1045#1]
FM25V02@TDFN8 [DX0001]
FM25V05@SOIC8 [DX1045#1]
FM25V10@SOIC8 [DX1045#1]
FM25V20@SOIC8 [DX1045#1]
FM25V20@TDFN8 [DX4005#1]
FM25W256@SOIC8 [DX1045#1]
FM28V020@SOIC28 [DX1033]
FM28V020@TSOP32 [DX1053]
FM28V100@TSOP32 [DX1053]
FM28V200@TSOP32 [DX1053]
FM30C256@SOIC20 [DX1033]
FM3104@SOIC14 [DX1030]
FM3116@SOIC14 [DX1030]
FM31256@SOIC14 [DX1016]
FM3164@SOIC14 [DX1016]
FM31L278@SOIC14 [DX1016]
FM33256B [DX0001]
FM33256B@SOIC14 [DX1045]
FM3808 [DX0001]
FM3808@TSOP32 [DX1003]

MICROCONTROLLER

VMX51C900 [DX0001]
VMX51C900@PLCC44 [DX2044]
VMX51C900@TQFP44 [DX3003]
VRS1000 [DX0001]
VRS1000@PLCC44 [DX2044]
VRS1000@TQFP44 [DX3003]
VRS1100 [DX0001]
VRS1100@PLCC44 [DX2044]
VRS1100@TQFP44 [DX3003]
VRS51C1000 [DX0001]
VRS51C1000@PLCC44 [DX2044]
VRS51C1000@TQFP44 [DX3003]
VRS51C1100 [DX0001]
VRS51C1100@PLCC44 [DX2044]
VRS51C1100@TQFP44 [DX3003]
VRS51C540 [DX0001]
VRS51C540@PLCC44 [DX2044]
VRS51C540@TQFP44 [DX3003]
VRS51C550 [DX0001]
VRS51C550@PLCC44 [DX2044]
VRS51C550@TQFP44 [DX3003]
VRS51C560 [DX0001]
VRS51C560@PLCC44 [DX2044]
VRS51C560@TQFP44 [DX3003]
VRS51C570 [DX0001]
VRS51C570@PLCC44 [DX2044]
VRS51C570@TQFP44 [DX3003]
VRS51C580 [DX0001]
VRS51C580@PLCC44 [DX2044]
VRS51C580@TQFP44 [DX3003]
VRS51C700 [DX0001]
VRS51C700@PLCC44 [DX2044]
VRS51C700@TQFP44 [DX3003]
VRS51L1050 [DX0001]
VRS51L1050@PLCC44 [DX2044]
VRS51L1050@TQFP44 [DX3003]
VRS51L540 [DX0001]
VRS51L540@PLCC44 [DX2044]
VRS51L540@TQFP44 [DX3003]
VRS51L550 [DX0001]
VRS51L550@PLCC44 [DX2044]
VRS51L550@TQFP44 [DX3003]
VRS51L560 [DX0001]
VRS51L560@PLCC44 [DX2044]
VRS51L560@TQFP44 [DX3003]
VRS51L570 [DX0001]
VRS51L570@PLCC44 [DX2044]
VRS51L570@TQFP44 [DX3003]

VRS51L580 [DX0001]
VRS51L580@PLCC44 [DX2044]
VRS51L580@TQFP44 [DX3003]
VRS51X540 [DX0001]
VRS51X540@PLCC44 [DX2044]
VRS51X540@TQFP44 [DX3003]
VRS51X550 [DX0001]
VRS51X550@PLCC44 [DX2044]
VRS51X550@TQFP44 [DX3003]
VRS51X560 [DX0001]
VRS51X560@PLCC44 [DX2044]
VRS51X560@TQFP44 [DX3003]
VRS51X570 [DX0001]
VRS51X570@PLCC44 [DX2044]
VRS51X570@TQFP44 [DX3003]
VRS51X580 [DX0001]
VRS51X580@PLCC44 [DX2044]
VRS51X580@TQFP44 [DX3003]
VRS540 [DX0001]
VRS540@PLCC44 [DX2044]
VRS540@TQFP44 [DX3003]
VRS550 [DX0001]
VRS550@PLCC44 [DX2044]
VRS550@TQFP44 [DX3003]
VRS560 [DX0001]
VRS560@PLCC44 [DX2044]
VRS560@TQFP44 [DX3003]
VRS570 [DX0001]
VRS570@PLCC44 [DX2044]
VRS570@TQFP44 [DX3003]
VRS580 [DX0001]
VRS580@PLCC44 [DX2044]
VRS580@TQFP44 [DX3003]
VRS700 [DX0001]
VRS700@PLCC44 [DX2044]
VRS700@TQFP44 [DX3003]
VRS900 [DX0001]
VRS900@PLCC44 [DX2044]
VRS900@TQFP44 [DX3003]

RATO

E(E)PROM/FRAM/NVRAM

RT24A02 [DX0001]
RT24A02@SOIC8 [DX1045]
RT24A02@TSSOP8 [DX1059]
RT24A04 [DX0001]
RT24A04@SOIC8 [DX1045]
RT24A04@TSSOP8 [DX1059]
RT24A08 [DX0001]
RT24A08@SOIC8 [DX1045]
RT24A08@TSSOP8 [DX1059]
RT24A16 [DX0001]
RT24A16@SOIC8 [DX1045]
RT24A16@TSSOP8 [DX1059]
RT93C46B(16bit) [DX0001]
RT93C46B(16bit)@SOIC8 [DX1045]
RT93C46B(16bit)@TSSOP8 [DX1059]
RT93LC46(08bit) [DX0001]
RT93LC46(08bit)@SOIC8 [DX1045]
RT93LC46(08bit)@TSSOP8 [DX1059]
RT93LC46(16bit) [DX0001]
RT93LC46(16bit)@SOIC8 [DX1045]
RT93LC46(16bit)@TSSOP8 [DX1059]

RAYDIUM

E(E)PROM/FRAM/NVRAM

RM24C02@SOP8 [DX1045]
RM24C04@SOP8 [DX1045]
RM24C08@SOP8 [DX1045]
RM24C128@SOP8 [DX1045]
RM24C16@SOP8 [DX1045]
RM24C32@SOP8 [DX1045]
RM24C64@SOP8 [DX1045]

REALTEK

MICROCONTROLLER

RTD2120L@LQFP48 [DX3007]
RTD2120L@PLCC44 [DX2044]

RENESAS

E(E)PROM/FRAM/NVRAM

HN58C256A(FP)@SOP28 [DX1033]
HN58C256A(P) [DX0001]
HN58C256A(T)@TSOP28 [DX1024]
HN58C257A(T)@TSOP32 [DX1003]
HN58V24256 [DX0001]
HN58V24256@SOIC8 [DX1045]
HN58V24256@TSSOP14 [DX1000]
HN58V24512 [DX0001]
HN58V24512@SOIC8 [DX1045]
HN58W241000 [DX0001]
HN58W241000@SOIC8 [DX1045]
HN58X2402 [DX0001]
HN58X2402@SOIC8 [DX1045]
HN58X2402@TSSOP8 [DX1059]
HN58X2404 [DX0001]
HN58X2404@SOIC8 [DX1045]
HN58X2404@TSSOP8 [DX1059]
HN58X2408 [DX0001]
HN58X2408@SOIC8 [DX1045]
HN58X2408@TSSOP8 [DX1059]
HN58X24128 [DX0001]
HN58X24128@SOIC8 [DX1045]
HN58X2416 [DX0001]
HN58X2416@SOIC8 [DX1045]
HN58X2416@TSSOP8 [DX1059]
HN58X24256 [DX0001]
HN58X24256@SOIC8 [DX1045]
HN58X2432 [DX0001]
HN58X2432@SOIC8 [DX1045]
HN58X2432@TSSOP8 [DX1059]
HN58X24512 [DX0001]
HN58X24512@SOIC8 [DX1045]
HN58X2464 [DX0001]
HN58X2464@SOIC8 [DX1045]
HN58X2464@TSSOP8 [DX1059]
HN58X2502@SOIC8 [DX1045]
HN58X2502@TSSOP8 [DX1059]
HN58X2504@SOIC8 [DX1045]
HN58X2504@TSSOP8 [DX1059]
HN58X2508@SOIC8 [DX1045]
HN58X2508@TSSOP8 [DX1059]
HN58X25128@SOIC8 [DX1045]
HN58X25128@TSSOP14 [DX1000]
HN58X2516@SOIC8 [DX1045]
HN58X2516@TSSOP8 [DX1059]
HN58X25256@SOIC8 [DX1045]
HN58X25256@TSSOP14 [DX1000]
HN58X2532@SOIC8 [DX1045]
HN58X2532@TSSOP8 [DX1059]
HN58X2564@SOIC8 [DX1045]
HN58X2564@TSSOP8 [DX1059]
M5L2732 [DX0001]
M5L2732A [DX0001]
M5M29KB331(AVP)@TSOP48 [DX1004]
M5M29KB641(AVP)@TSOP48 [DX1004]
M5M29KE131BTP@TSOP52 [DX1009]
M5M29KE131BV@TSOP48 [DX1004]
M5M29KT331(AVP)@TSOP48 [DX1004]
M5M29KT641(AVP)@TSOP48 [DX1004]
M6MG3B641S16TP@TSOP52 [DX1009]
M6MG3T641S16TP@TSOP52 [DX1009]
M6MGB166S4B(WG)@FBGA72 [DX5001]
M6MGB321S4TP@TSOP52 [DX1009]
M6MGB321S8TP@TSOP52 [DX1009]
M6MGB32BS4WG@CSP66 [DX5001]
M6MGB32BS8WG@CSP66 [DX5001]
M6MGB331S8KT@TSOP52 [DX1009]
M6MGB33BS8AWG@CSP66 [DX5001]
M6MGB641S16TP@TSOP52 [DX1009]
M6MGB641S4TP@TSOP52 [DX1009]
M6MGB641S8TP@TSOP52 [DX1009]
M6MGB647M34CKT@TSOP52 [DX1009]

M6MGB64BM17AWG@CSP67 [DX5053]
M6MGB64BM34CDG@CSP88 [DX5053]
M6MGB64BM34CWG@CSP67 [DX5053]
M6MGB64BS4WG@CSP67 [DX5001]
M6MGB64BS8WG@CSP67 [DX5001]
M6MGD137W33(WG)@CSP72 [DX5053]
M6MGD13TW34DWG@CSP72 [DX5053]
M6MGE157S4KT@TSOP52 [DX1009]
M6MGT166S4B(WG)@FBGA72 [DX5001]
M6MGT321S4TP@TSOP52 [DX1009]
M6MGT321S8TP@TSOP52 [DX1009]
M6MGT32BS4WG@CSP66 [DX5001]
M6MGT32BS8WG@CSP66 [DX5001]
M6MGT331S8KT@TSOP52 [DX1009]
M6MGT33BS8AWG@CSP66 [DX5001]
M6MGT641S16TP@TSOP52 [DX1009]
M6MGT641S4TP@TSOP52 [DX1009]
M6MGT641S8TP@TSOP52 [DX1009]
M6MGT647M34CKT@TSOP52 [DX1009]
M6MGT64BM17AWG@CSP67 [DX5053]
M6MGT64BM34CDG@CSP88 [DX5053]
M6MGT64BM34CWG@CSP67 [DX5053]
M6MGT64BS4WG@CSP67 [DX5001]
M6MGT64BS8WG@CSP67 [DX5001]
MC10233@BGA208 [DX5226#1]
MC10256@BGA208 [DX5226#1]
R1EX24002A@SOP8 [DX1045]
R1EX24002A@TSSOP8 [DX1059]
R1EX24004A@SOP8 [DX1045]
R1EX24004A@TSSOP8 [DX1059]
R1EX24008A@SOP8 [DX1045]
R1EX24008A@TSSOP8 [DX1059]
R1EX24016A@SOP8 [DX1045]
R1EX24016A@TSSOP8 [DX1059]
R1EX24032A@SOP8 [DX1045]
R1EX24032A@TSSOP8 [DX1059]
R1EX24064A@SOP8 [DX1045]
R1EX24064A@TSSOP8 [DX1059]
R1EX24128A@SOP8 [DX1045]
R1EX24128A@TSSOP8 [DX1059]
R1EX24256A@SOP8 [DX1045]
R1EX24256A@TSSOP8 [DX1059]
R1EX24512A@SOP8 [DX1045]
R1EX24512A@TSSOP8 [DX1059]
R1EX25002A@SOIC8 [DX1045]
R1EX25002A@TSSOP8 [DX1059]
R1EX25004A@SOIC8 [DX1045]
R1EX25004A@TSSOP8 [DX1059]
R1EX25008A@SOIC8 [DX1045]
R1EX25008A@TSSOP8 [DX1059]
R1EX25016A@SOIC8 [DX1045]
R1EX25016A@TSSOP8 [DX1059]
R1EX25032A@SOIC8 [DX1045]
R1EX25032A@TSSOP8 [DX1059]
R1EX25064A@SOIC8 [DX1045]
R1EX25064A@TSSOP8 [DX1059]

DRAM & SRAM

R1LV0408C@SOP32 [DX1020]
R1LV0408C@STSOP32 [DX1003]
R1LV0408C@TSOP32 [DX1002]

MICROCONTROLLER

HD6472246FA@QFP100 [DX3043]
HD6472357F@PQFP128 [DX3031]
HD6472357TE@QFP120 [DX3027]
HD6472655F@PQFP128 [DX3031]
HD6472655TE@QFP120 [DX3027]
HD6472655VF@PQFP128 [DX3031]
HD6472655VTE@QFP120 [DX3027]
HD6473032F@QFP80 [DX3018]
HD6473032TF@QFP80 [DX3016]
HD6473042F@QFP100 [DX3043]
HD6473042TF@TQFP100 [DX3043]
HD6473042VF@QFP100 [DX3043]
HD6473042VTF@TQFP100 [DX3043]
HD6473228CP@PLCC68 [DX2068]
HD6473228F@QFP64 [DX3014]
HD6473228P@SDIP64 [DX0064]
HD6473238CP@PLCC68 [DX2068]
HD6473238F@QFP64 [DX3014]
HD6473238P@SDIP64 [DX0064]
HD6473256CP@PLCC68 [DX2068]

HD6473256F@QFP64 [DX3014]
HD6473256P@SDIP64 [DX0064]
HD6473257C@SDIP64 [DX0064]
HD6473257CP@PLCC68 [DX2068]
HD6473257F@QFP64 [DX3014]
HD6473257P@SDIP64 [DX0064]
HD6473258C@SDIP64 [DX0064]
HD6473258CP@PLCC68 [DX2068]
HD6473258F@QFP64 [DX3014]
HD6473258P@SDIP64 [DX0064]
HD6473308CG@PLCC84 [DX2084]
HD6473308CP@PLCC84 [DX2084]
HD6473308F@QFP80 [DX3018]
HD6473334YCP@PLCC84 [DX2084]
HD6473334YF@QFP80 [DX3018]
HD6473334YTF@QFP80 [DX3016]
HD6473337YCG@PLCC84 [DX2084]
HD6473337YCP@PLCC84 [DX2084]
HD6473337YF@QFP80 [DX3018]
HD6473337YTF@QFP80 [DX3016]
HD6473378CP@PLCC84 [DX2084]
HD6473644H [DX3014]
HD6473644RH [DX3014]
HD64738024F@PQFP80 [DX3019]
HD64738024H@QFP80 [DX3018]
HD64738024W@QFP80 [DX3016]
HD6473834D@QFP100 [DX3043]
HD6473834E@PQFP100 [DX3023]
HD6473834F@PQFP100 [DX3023]
HD6473834H@QFP100 [DX3043]
HD6473834X@QFP100 [DX3043]
HD6473837D@QFP100 [DX3043]
HD6473837E@PQFP100 [DX3023]
HD6473837F@PQFP100 [DX3023]
HD6473837H@QFP100 [DX3043]
HD6473837X@QFP100 [DX3043]
HD6473877H@QFP100 [DX3043]
HD6475208C@SDIP64 [DX0064]
HD6475208P@SDIP64 [DX0064]
HD6475328CG@PLCC84 [DX2084]
HD6475328CP@PLCC84 [DX2084]
HD6475328F@QFP80 [DX3018]
HD6475348CG@PLCC84 [DX2084]
HD6475348CP@PLCC84 [DX2084]
HD6475348F@QFP80 [DX3018]
HD6475348RCG@PLCC84 [DX2084]
HD6475348RCP@PLCC84 [DX2084]
HD6475348RF@QFP80 [DX3018]
HD6475348SCG@PLCC84 [DX2084]
HD6475348SCP@PLCC84 [DX2084]
HD6475348SF@QFP80 [DX3018]
HD6475368CG@PLCC84 [DX2084]
HD6475368CP@PLCC84 [DX2084]
HD6475368F@QFP80 [DX3018]
HD6475368RCG@PLCC84 [DX2084]
HD6475368RCP@PLCC84 [DX2084]
HD6475368RF@QFP80 [DX3018]
HD6475368SCG@PLCC84 [DX2084]
HD6475368SCP@PLCC84 [DX2084]
HD6475368SF@QFP80 [DX3018]
HD6475708F [DX3025]
HD6477034F@QFP112 [DX3025]
HD6477042F@QFP112 [DX3025]
HD6477043F@QFP144 [DX3035]
HD64F2110BFA@QFP100 [DX3021]
HD64F2110BTE@QFP100 [DX3021]
HD64F2110BVFA@QFP100 [DX3021]
HD64F2110BVTE@QFP100 [DX3021]
HD64F2111BVTE@QFP144 [DX3041]
HD64F2132RFA20@QFP80 [DX3018]
HD64F2132RTF10@QFP80 [DX3016]
HD64F2132RVFA10@QFP80 [DX3018]
HD64F2132RVTF10@QFP80 [DX3016]
HD64F2134AFA20@QFP80 [DX3018]
HD64F2134ATF10@QFP80 [DX3016]
HD64F2134AVFA10@QFP80 [DX3018]
HD64F2134AVTF10@QFP80 [DX3016]
HD64F2134FA20@QFP80 [DX3018]
HD64F2134TF10@QFP80 [DX3016]
HD64F2134VFA10@QFP80 [DX3018]
HD64F2134VTF10@QFP80 [DX3016]
HD64F2138AFA20@QFP80 [DX3018]
HD64F2138ATF10@QFP80 [DX3016]
HD64F2138AVFA10@QFP80 [DX3018]
HD64F2138AVTF10@QFP80 [DX3016]
HD64F2138FA20@QFP80 [DX3018]
HD64F2138TF10@QFP80 [DX3016]
HD64F2138VFA10@QFP80 [DX3018]
HD64F2138VTF10@QFP80 [DX3016]
HD64F2140BVFA10@QFP100 [DX3021]
HD64F2140BVTE10@QFP100 [DX3021]
HD64F2141BVFA10@QFP100 [DX3021]
HD64F2141BVTE10@QFP100 [DX3021]
HD64F2142RFA20@QFP100 [DX3021]
HD64F2142RTE20@QFP100 [DX3021]
HD64F2142RVFA10@QFP100 [DX3021]

HD64F2142RVTE10@QFP100 [DX3021]
HD64F2144ATE20@QFP100 [DX3021]
HD64F2144AVTE10@QFP100 [DX3021]
HD64F2144TE20@QFP100 [DX3021]
HD64F2144VTE10@QFP100 [DX3021]
HD64F2145BVTE10@QFP100 [DX3021]
HD64F2147ATE20@QFP100 [DX3021]
HD64F2147AVTE10@QFP100 [DX3021]
HD64F2147NTE20@QFP100 [DX3021]
HD64F2147NVTE10@QFP100 [DX3021]
HD64F2148ATE20@QFP100 [DX3021]
HD64F2148AVTE10@QFP100 [DX3021]
HD64F2148BTE20@QFP100 [DX3021]
HD64F2148BVTE10@QFP100 [DX3021]
HD64F2148TE20@QFP100 [DX3021]
HD64F2148VTE10@QFP100 [DX3021]
HD64F2149YTE20@QFP100 [DX3021]
HD64F2149YVTE10@QFP100 [DX3021]
HD64F2160BVTE10@QFP144 [DX3041]
HD64F2161BVTE10@QFP144 [DX3041]
HD64F2167VTE33@TQFP144 [DX3034]
HD64F2169YTE20@QFP144 [DX3041]
HD64F2177VTE33@TQFP144 [DX3034]
HD64F2210FP [DX3011]
HD64F2211CUFP [DX3011]
HD64F2211UFP [DX3011]
HD64F2212FP [DX3011]
HD64F2215RTE@QFP120 [DX3027]
HD64F2215TE@QFP120 [DX3027]
HD64F2215TUTE@QFP120 [DX3027]
HD64F2218TF@QFP100 [DX3071]
HD64F2238ATE@TQFP100 [DX3043]
HD64F2238BFA@QFP100 [DX3043]
HD64F2238BTF@TQFP100 [DX3071]
HD64F2238RBR@FBGA112 [DX5058]
HD64F2238RFA@QFP100 [DX3043]
HD64F2238RTF@TQFP100 [DX3071]
HD64F2239F@PQFP100 [DX3022]
HD64F2239TE@TQFP100 [DX3043]
HD64F2258F@PQFP100 [DX3022]
HD64F2258TE@TQFP100 [DX3043]
HD64F2265TE@TQFP100 [DX3043]
HD64F2266FA@TQFP100 [DX3043]
HD64F2266TF@TQFP100 [DX3071]
HD64F2268TE@TQFP100 [DX3043]
HD64F2280F20B@QFP100 [DX3022]
HD64F2282F20@QFP100 [DX3022]
HD64F2314VTE@QFP100 [DX3043]
HD64F2144AFA20@QFP100 [DX3021]
HD64F2144AVFA10@QFP100 [DX3021]
HD64F2144FA20@QFP100 [DX3021]
HD64F2144VFA10@QFP100 [DX3021]
HD64F2145BVFA10@QFP100 [DX3021]
HD64F2147AFA20@QFP100 [DX3021]
HD64F2147AVFA10@QFP100 [DX3021]
HD64F2147NFA20@QFP100 [DX3021]
HD64F2147NVFA10@QFP100 [DX3021]
HD64F2148AFA20@QFP100 [DX3021]
HD64F2148AVFA10@QFP100 [DX3021]
HD64F2148BFA20@QFP100 [DX3021]
HD64F2148BVFA10@QFP100 [DX3021]
HD64F2148FA20@QFP100 [DX3021]
HD64F2148VFA10@QFP100 [DX3021]
HD64F2149YFA20@QFP100 [DX3021]
HD64F2149YVFA10@QFP100 [DX3021]
HD64F2160BTE20@QFP144 [DX3041]
HD64F2161BTE20@QFP144 [DX3041]
HD64F2166VTE33@TQFP144 [DX3034]
HD64F2168VTE33@TQFP144 [DX3034]
HD64F2169YVTE10@QFP144 [DX3041]
HD64F2210CUFP [DX3011]
HD64F2210UFP [DX3011]
HD64F2211FP [DX3011]
HD64F2212CUFP [DX3011]
HD64F2212UFP [DX3011]
HD64F2215RUTE@QFP120 [DX3027]
HD64F2215TTE@QFP120 [DX3027]
HD64F2215UTE@QFP120 [DX3027]
HD64F2218UTF@QFP100 [DX3071]
HD64F2238BF@PQFP100 [DX3022]
HD64F2238BTE@TQFP100 [DX3043]
HD64F2238RBQ@FBGA112 [DX5058]
HD64F2238RF@PQFP100 [DX3022]
HD64F2238RTE@TQFP100 [DX3043]
HD64F2239BQ@FBGA112 [DX5058]
HD64F2239FA@QFP100 [DX3043]
HD64F2239TF@TQFP100 [DX3071]
HD64F2258FA@QFP100 [DX3043]
HD64F2265FA@TQFP100 [DX3043]
HD64F2265TF@TQFP100 [DX3071]
HD64F2266TE@TQFP100 [DX3043]
HD64F2268FA@TQFP100 [DX3043]
HD64F2268TF@TQFP100 [DX3071]
HD64F2280F20RB@QFP100 [DX3022]
HD64F2314VF@PQFP100 [DX3022]
HD64F2315VF@PQFP100 [DX3022]

HD64F2315VTE@QFP100 [DX3043]
HD64F2317VF@PQFP100 [DX3022]
HD64F2317VTE@QFP100 [DX3043]
HD64F2317VTF@QFP100 [DX3043]
HD64F2318VF@PQFP100 [DX3022]
HD64F2318VTE@QFP100 [DX3043]
HD64F2318VTF@QFP100 [DX3043]
HD64F2319EVF@PQFP100 [DX3022]
HD64F2319EVTE@QFP100 [DX3043]
HD64F2319VF@PQFP100 [DX3022]
HD64F2319VTE@QFP100 [DX3043]
HD64F2326VF@PQFP128 [DX3032]
HD64F2326VTE@QFP120 [DX3027]
HD64F2328BVF@PQFP128 [DX3032]
HD64F2328BVTE@QFP120 [DX3027]
HD64F2329BVF@PQFP128 [DX3032]
HD64F2329BVTE@QFP120 [DX3027]
HD64F2329EVF@PQFP128 [DX3032]
HD64F2329EVTE@QFP120 [DX3027]
HD64F2338VFC@QFP144 [DX3035]
HD64F2339EVFC@QFP144 [DX3035]
HD64F2339VFC@QFP144 [DX3035]
HD64F2345F@PQFP100 [DX3022]
HD64F2345FA@QFP100 [DX3043]
HD64F2345TE@QFP100 [DX3043]
HD64F2345TF@QFP100 [DX3071]
HD64F2357F@PQFP128 [DX3032]
HD64F2357TE@QFP120 [DX3027]
HD64F2360VTE@QFP120 [DX3030]
HD64F2361VTE@QFP120 [DX3030]
HD64F2362VTE@QFP120 [DX3030]
HD64F2364VTE@QFP120 [DX3030]
HD64F2368VTE@QFP120 [DX3030]
HD64F2370RVFQ@QFP144 [DX3035]
HD64F2370VFQ@QFP144 [DX3035]
HD64F2371RVFQ@QFP144 [DX3035]
HD64F2371VFQ@QFP144 [DX3035]
HD64F2372RVFQ@QFP144 [DX3035]
HD64F2372VFQ@QFP144 [DX3035]
HD64F2374RVFQ@QFP144 [DX3035]
HD64F2374VFQ@QFP144 [DX3035]
HD64F2376VFQ@QFP144 [DX3035]
HD64F2377RVFQ@QFP144 [DX3035]
HD64F2377VFQ@QFP144 [DX3035]
HD64F2378BVFQ@QFP144 [DX3035]
HD64F2378RVFQ@QFP144 [DX3035]
HD64F2398F@PQFP128 [DX3032]
HD64F2398FT@PQFP128 [DX3032]
HD64F2398TE@QFP120 [DX3027]
HD64F2398TET@QFP120 [DX3027]
HD64F2505FC26@QFP144 [DX3051]
HD64F2506FC26@QFP144 [DX3051]
HD64F2551FC26@QFP144 [DX3051]
HD64F2552FC26@QFP144 [DX3051]
HD64F2556FC20@QFP144 [DX3051]
HD64F2612FA20@QFP80 [DX3018]
HD64F2615F20@QFP80 [DX3018]
HD64F2615F24@QFP80 [DX3018]
HD64F2623FA@QFP100 [DX3043]
HD64F2626FA@QFP100 [DX3043]
HD64F2628FA@QFP100 [DX3043]
HD64F2630F@PQFP128 [DX3032]
HD64F2630UF@PQFP128 [DX3032]
HD64F2630WF@PQFP128 [DX3032]
HD64F2633F@PQFP128 [DX3032]
HD64F2633RF@PQFP128 [DX3032]
HD64F2633RTE@QFP120 [DX3027]
HD64F2633TE@QFP120 [DX3027]
HD64F2635F@PQFP128 [DX3032]
HD64F2636F@PQFP128 [DX3032]
HD64F2636UF@PQFP128 [DX3032]
HD64F2638F@PQFP128 [DX3032]
HD64F2638UF@PQFP128 [DX3032]
HD64F2638WF@PQFP128 [DX3032]
HD64F2639UF@PQFP128 [DX3032]
HD64F2639WF@PQFP128 [DX3032]
HD64F2643FC25@QFP144 [DX3035]
HD64F2646RFC20@QFP144 [DX3035]
HD64F2648RFC20@QFP144 [DX3035]
HD64F2649FC20@QFP144 [DX3035]
HD64F2667VFQ33@QFP144 [DX3035]
HD64F2676VF@QFP144 [DX3035]
HD64F3024F@TQFP100 [DX3021]
HD64F3024FP@PQFP100 [DX3022]
HD64F3024TE@TQFP100 [DX3021]
HD64F3026F@QFP100 [DX3021]
HD64F3026FP@PQFP100 [DX3022]
HD64F3026TE@TQFP100 [DX3021]
HD64F3029F@QFP100 [DX3043]
HD64F3029TE@TQFP100 [DX3043]
HD64F3039F@QFP80 [DX3018]
HD64F3039TE@TQFP80 [DX3016]
HD64F3039VF@QFP80 [DX3018]
HD64F3039VTE@TQFP80 [DX3016]
HD64F3048BF@TQFP100 [DX3021]
HD64F3048BTE@TQFP100 [DX3021]

HD64F3048BVF@TQFP100 [DX3021]
HD64F3048BVTE@TQFP100 [DX3021]
HD64F3048F@TQFP100 [DX3021]
HD64F3048TF@TQFP100 [DX3021]
HD64F3048VF@TQFP100 [DX3021]
HD64F3048VTF@TQFP100 [DX3021]
HD64F3052BF@TQFP100 [DX3021]
HD64F3052BTE@TQFP100 [DX3021]
HD64F3052BVF@TQFP100 [DX3021]
HD64F3052BVTE@TQFP100 [DX3021]
HD64F3052F@TQFP100 [DX3021]
HD64F3052TE@TQFP100 [DX3021]
HD64F3062BF@TQFP100 [DX3021]
HD64F3062BFP@PQFP100 [DX3022]
HD64F3062BTE@TQFP100 [DX3021]
HD64F3062F@TQFP100 [DX3021]
HD64F3062FP@PQFP100 [DX3022]
HD64F3062RF@TQFP100 [DX3021]
HD64F3062RFP@PQFP100 [DX3022]
HD64F3062RTE@TQFP100 [DX3021]
HD64F3062RVF@TQFP100 [DX3021]
HD64F3062RVFP@PQFP100 [DX3022]
HD64F3062RVTE@TQFP100 [DX3021]
HD64F3062TE@TQFP100 [DX3021]
HD64F3062VF@TQFP100 [DX3021]
HD64F3062VFP@TQFP100 [DX3022]
HD64F3062VTE@TQFP100 [DX3021]
HD64F3064BF@TQFP100 [DX3021]
HD64F3064BFP@PQFP100 [DX3022]
HD64F3064BTE@TQFP100 [DX3021]
HD64F3064F@TQFP100 [DX3021]
HD64F3064FP@PQFP100 [DX3022]
HD64F3064TE@TQFP100 [DX3021]
HD64F3067F@TQFP100 [DX3021]
HD64F3067FP@PQFP100 [DX3022]
HD64F3067RF@TQFP100 [DX3021]
HD64F3067RFP@PQFP100 [DX3022]
HD64F3067RTE@TQFP100 [DX3021]
HD64F3067RVF@TQFP100 [DX3021]
HD64F3067RVFP@PQFP100 [DX3022]
HD64F3067RVTE@TQFP100 [DX3021]
HD64F3067TE@TQFP100 [DX3021]
HD64F3067VF@TQFP100 [DX3021]
HD64F3067VFP@TQFP100 [DX3022]
HD64F3067VTE@TQFP100 [DX3021]
HD64F3068F@TQFP100 [DX3021]
HD64F3068TE@TQFP100 [DX3021]
HD64F3069F@TQFP100 [DX3043]
HD64F3069TE@TQFP100 [DX3043]
HD64F3334YCP@PLCC84 [DX2084]
HD64F3334YF@TQFP80 [DX3018]
HD64F3334YFLH@TQFP80 [DX3018]
HD64F3334YTF@TQFP80 [DX3016]
HD64F3334YTFLH@TQFP80 [DX3016]
HD64F3337YCP@PLCC84 [DX2084]
HD64F3337YF@TQFP80 [DX3018]
HD64F3337YFLH@TQFP80 [DX3018]
HD64F3337YTF@TQFP80 [DX3016]
HD64F3337YTFLH@TQFP80 [DX3016]
HD64F3394YCP@PLCC84 [DX2084]
HD64F3394YF@TQFP80 [DX3018]
HD64F3394YFLH@TQFP80 [DX3018]
HD64F3394YTF@TQFP80 [DX3016]
HD64F3394YTFLH@TQFP80 [DX3016]
HD64F3397CP@PLCC84 [DX2084]
HD64F3397F@TQFP80 [DX3018]
HD64F3397FLH@TQFP80 [DX3018]
HD64F3397TF@TQFP80 [DX3016]
HD64F3397TFLH@TQFP80 [DX3016]
HD64F3434F@TQFP100 [DX3021]
HD64F3434FLH@TQFP100 [DX3021]
HD64F3434TF@TQFP100 [DX3021]
HD64F3434TFLH@TQFP100 [DX3021]
HD64F3437F@TQFP100 [DX3021]
HD64F3437FLH@TQFP100 [DX3021]
HD64F3437TF@TQFP100 [DX3021]
HD64F3437TFLH@TQFP100 [DX3021]
HD64F36012FP@QFP64 [DX3011]
HD64F36012FT@QFN48 [DX4021]
HD64F36012FX@QFP48 [DX3008]
HD64F36012FY@QFP48 [DX3007]
HD64F36012GFP@QFP64 [DX3011]
HD64F36012GFT@QFN48 [DX4021]
HD64F36012GFX@QFP48 [DX3008]
HD64F36012GFY@QFP48 [DX3007]
HD64F36014FP@QFP64 [DX3011]
HD64F36014FT@QFN48 [DX4021]
HD64F36014FX@QFP48 [DX3008]
HD64F36014FY@QFP48 [DX3007]
HD64F36014GFP@QFP64 [DX3011]
HD64F36014GFT@QFN48 [DX4021]
HD64F36014GFX@QFP48 [DX3008]
HD64F36014GFY@QFP48 [DX3007]
HD64F36022FP@QFP64 [DX3011]
HD64F36022FT@QFN48 [DX4021]
HD64F36022FX@QFP48 [DX3008]

HD64F36022FY@QFP48 [DX3007]
HD64F36022GFP@QFP64 [DX3011]
HD64F36022GFT@QFN48 [DX4021]
HD64F36022GFX@QFP48 [DX3008]
HD64F36022GFY@QFP48 [DX3007]
HD64F36024FP@QFP64 [DX3011]
HD64F36024FT@QFN48 [DX4021]
HD64F36024FX@QFP48 [DX3008]
HD64F36024FY@QFP48 [DX3007]
HD64F36024GFP@QFP64 [DX3011]
HD64F36024GFT@QFN48 [DX4021]
HD64F36024GFX@QFP48 [DX3008]
HD64F36024GFY@QFP48 [DX3007]
HD64F36034FZ@QFP64 [DX3011]
HD64F36034GFZ@QFP64 [DX3011]
HD64F36034GH@QFP64 [DX3014]
HD64F36034H@QFP64 [DX3014]
HD64F36037FZ@QFP64 [DX3011]
HD64F36037GFZ@QFP64 [DX3011]
HD64F36037GH@QFP64 [DX3014]
HD64F36037H@QFP64 [DX3014]
HD64F36049GH@QFP80 [DX3018]
HD64F36049H@QFP80 [DX3018]
HD64F36054FZ@QFP64 [DX3011]
HD64F36054GFZ@QFP64 [DX3011]
HD64F36054GH@QFP64 [DX3014]
HD64F36054H@QFP64 [DX3014]
HD64F36057FZ@QFP64 [DX3011]
HD64F36057GFZ@QFP64 [DX3011]
HD64F36057GH@QFP64 [DX3014]
HD64F36057H@QFP64 [DX3014]
HD64F36064FP@QFP64 [DX3011]
HD64F36064GFP@QFP64 [DX3011]
HD64F36064GH@QFP64 [DX3014]
HD64F36064H@QFP64 [DX3014]
HD64F36074GFZ@QFP64 [DX3011]
HD64F36074GFZW@QFP64 [DX3011]
HD64F36074GH@QFP64 [DX3014]
HD64F36074GHV@QFP64 [DX3014]
HD64F36074GHW@QFP64 [DX3014]
HD64F36074GHZ@QFP64 [DX3014]
HD64F36074GHZW@QFP64 [DX3014]
HD64F36074LFZ@QFP64 [DX3011]
HD64F36074LFZW@QFP64 [DX3011]
HD64F36074LH@QFP64 [DX3014]
HD64F36074LHV@QFP64 [DX3014]
HD64F36074LHW@QFP64 [DX3014]
HD64F36074LHZ@QFP64 [DX3014]
HD64F36074LHZW@QFP64 [DX3014]
HD64F36077GFZ@QFP64 [DX3011]
HD64F36077GFZW@QFP64 [DX3011]
HD64F36077GH@QFP64 [DX3014]
HD64F36077GHV@QFP64 [DX3014]
HD64F36077GHW@QFP64 [DX3014]
HD64F36077GHZ@QFP64 [DX3014]
HD64F36077GHZW@QFP64 [DX3014]
HD64F36077LFZ@QFP64 [DX3011]
HD64F36077LFZW@QFP64 [DX3011]
HD64F36077LH@QFP64 [DX3014]
HD64F36077LHV@QFP64 [DX3014]
HD64F36077LHW@QFP64 [DX3014]
HD64F36077LHZ@QFP64 [DX3014]
HD64F36077LHZW@QFP64 [DX3014]
HD64F36078GFZ@QFP64 [DX3011]
HD64F36078GFZW@QFP64 [DX3011]
HD64F36078GH@QFP64 [DX3014]
HD64F36078GHV@QFP64 [DX3014]
HD64F36078GHW@QFP64 [DX3014]
HD64F36078GHZ@QFP64 [DX3014]
HD64F36078GHZW@QFP64 [DX3014]
HD64F36078LFZ@QFP64 [DX3011]
HD64F36078LFZW@QFP64 [DX3011]
HD64F36078LH@QFP64 [DX3014]
HD64F36078LHV@QFP64 [DX3014]
HD64F36078LHW@QFP64 [DX3014]
HD64F36078LHZ@QFP64 [DX3014]
HD64F36078LHZW@QFP64 [DX3014]
HD64F36079GFZ@QFP64 [DX3011]
HD64F36079GFZW@QFP64 [DX3011]
HD64F36079GH@QFP64 [DX3014]
HD64F36079GHV@QFP64 [DX3014]
HD64F36079GHW@QFP64 [DX3014]
HD64F36079GHZ@QFP64 [DX3014]
HD64F36079GHZW@QFP64 [DX3014]
HD64F36079LFZ@QFP64 [DX3011]
HD64F36079LFZW@QFP64 [DX3011]
HD64F36079LH@QFP64 [DX3014]
HD64F36079LHV@QFP64 [DX3014]
HD64F36079LHW@QFP64 [DX3014]
HD64F36079LHZ@QFP64 [DX3014]
HD64F36079LHZW@QFP64 [DX3014]
HD64F36087FP@QFP64 [DX3011]
HD64F36087H@QFP64 [DX3014]
HD64F36109F@PQFP100 [DX3022]
HD64F36109GF@PQFP100 [DX3022]
HD64F36109GH@LQFP100 [DX3043]

HD64F36109H@LQFP100 [DX3043]
HD64F3642AH@TQFP64 [DX3014]
HD64F3642AP@SDIP64 [DX0064]
HD64F3642AW@TQFP80 [DX3016]
HD64F3643H@TQFP64 [DX3014]
HD64F3643P@SDIP64 [DX0064]
HD64F3643W@TQFP80 [DX3016]
HD64F3644H@TQFP64 [DX3014]
HD64F3644P@SDIP64 [DX0064]
HD64F3644W@TQFP80 [DX3016]
HD64F3664BP@SDIP42 [DX0042]
HD64F3664FP@QFP64 [DX3011]
HD64F3664FX@QFP48 [DX3008]
HD64F3664FY@QFP48 [DX3007]
HD64F3664GBP@SDIP42 [DX0042]
HD64F3664GFP@QFP64 [DX3011]
HD64F3664GFX@QFP48 [DX3008]
HD64F3664GFY@QFP48 [DX3007]
HD64F3664GH@QFP64 [DX3014]
HD64F3664H@QFP64 [DX3014]
HD64F3684FP@QFP64 [DX3011]
HD64F3684GFP@QFP64 [DX3011]
HD64F3684GH@QFP64 [DX3014]
HD64F3684H@QFP64 [DX3014]
HD64F3687FP@QFP64 [DX3011]
HD64F3687GFP@QFP64 [DX3011]
HD64F3687GH@QFP64 [DX3014]
HD64F3687H@QFP64 [DX3014]
HD64F36902GFH@QFP32 [DX3001]
HD64F36902GP@SDIP32 [DX0032]
HD64F36902GTP@SOP32 [DX1034]
HD64F36912GFH@QFP32 [DX3001]
HD64F36912GP@SDIP32 [DX0032]
HD64F36912GTP@SOP32 [DX1034]
HD64F3694FP@QFP64 [DX3011]
HD64F3694FX@QFP48 [DX3008]
HD64F3694FY@QFP48 [DX3007]
HD64F3694GFP@QFP64 [DX3011]
HD64F3694GFX@QFP48 [DX3008]
HD64F3694GFY@QFP48 [DX3007]
HD64F3694GH@QFP64 [DX3014]
HD64F3694H@QFP64 [DX3014]
HD64F38002FP@TQFP64 [DX3011]
HD64F38002H@TQFP64 [DX3014]
HD64F38004FP@TQFP64 [DX3011]
HD64F38004H@TQFP64 [DX3014]
HD64F38024F@QFP80 [DX3019]
HD64F38024H@QFP80 [DX3018]
HD64F38024RF@QFP80 [DX3019]
HD64F38024RH@QFP80 [DX3018]
HD64F38024RW@QFP80 [DX3016]
HD64F38024W@QFP80 [DX3016]
HD64F38102FP@TQFP64 [DX3011]
HD64F38102H@TQFP64 [DX3014]
HD64F38104FP@TQFP64 [DX3011]
HD64F38104H@TQFP64 [DX3014]
HD64F38124D@QFP80 [DX3018]
HD64F38124H@QFP80 [DX3018]
HD64F38124W@QFP80 [DX3016]
HD64F38124WI@QFP80 [DX3016]
HD64F38324H@QFP80 [DX3018]
HD64F38324HW@QFP80 [DX3018]
HD64F38324W@QFP80 [DX3016]
HD64F38324WW@QFP80 [DX3016]
HD64F38327H@QFP80 [DX3018]
HD64F38327HW@QFP80 [DX3018]
HD64F38327W@QFP80 [DX3016]
HD64F38327WW@QFP80 [DX3016]
HD64F38424H@QFP80 [DX3018]
HD64F38424HW@QFP80 [DX3018]
HD64F38424W@QFP80 [DX3016]
HD64F38424WW@QFP80 [DX3016]
HD64F38427H@QFP80 [DX3018]
HD64F38427HW@QFP80 [DX3018]
HD64F38427W@QFP80 [DX3016]
HD64F38427WW@QFP80 [DX3016]
HD64F39012FP@QFP64 [DX3011]
HD64F39012FT@QFN48 [DX4021]
HD64F39012FX@QFP48 [DX3008]
HD64F39012FY@QFP48 [DX3007]
HD64F39012GFP@QFP64 [DX3011]
HD64F39012GFT@QFN48 [DX4021]
HD64F39012GFX@QFP48 [DX3008]
HD64F39012GFY@QFP48 [DX3007]
HD64F39014FP@QFP64 [DX3011]
HD64F39014FT@QFN48 [DX4021]
HD64F39014FX@QFP48 [DX3008]
HD64F39014FY@QFP48 [DX3007]
HD64F39014GFP@QFP64 [DX3011]
HD64F39014GFT@QFN48 [DX4021]
HD64F39014GFX@QFP48 [DX3008]
HD64F39014GFY@QFP48 [DX3007]
HD64F39022FP@QFP64 [DX3011]
HD64F39022FT@QFN48 [DX4021]
HD64F39022FX@QFP48 [DX3008]
HD64F39022FY@QFP48 [DX3007]

HD64F39022GFP@QFP64 [DX3011]
HD64F39022GFT@QFN48 [DX4021]
HD64F39022GFX@QFP48 [DX3008]
HD64F39022GFY@QFP48 [DX3007]
HD64F39024FP@QFP64 [DX3011]
HD64F39024FT@QFN48 [DX4021]
HD64F39024FX@QFP48 [DX3008]
HD64F39024FY@QFP48 [DX3007]
HD64F39024GFP@QFP64 [DX3011]
HD64F39024GFT@QFN48 [DX4021]
HD64F39024GFX@QFP48 [DX3008]
HD64F39024GFY@QFP48 [DX3007]
HD64F39802GP@SDIP32 [DX0032]
HD64F7044F28@QFP112 [DX3025]
HD64F7045F28@QFP144 [DX3035]
HD64F7046F50@QFP80 [DX3018]
HD64F7047F50@QFP100 [DX3021]
HD64F7052F40@QFP208(*) [DX3059]
HD64F7053F40@QFP208(*) [DX3059]
HD64F7054F40@QFP208(*) [DX3059]
HD64F7055F40@PQFP256(*) [DX3070]
HD64F7058F80@PQFP256(*) [DX3070]
HD64F7065AF60@QFP176 [DX3099]
HD64F7065SF60@QFP176 [DX3099]
HD64F7144F50@QFP112 [DX3025]
HD64F7144FW50@QFP112 [DX3025]
HD64F7145F50@QFP144 [DX3035]
HD64F7145FW50@QFP144 [DX3035]
M30260F3AGP@QFP48 [DX3007]
M30260F3TGP@QFP48 [DX3007]
M30260F3VGP@QFP48 [DX3007]
M30260F6AGP@QFP48 [DX3007]
M30260F6TGP@QFP48 [DX3007]
M30260F6VGP@QFP48 [DX3007]
M30260F8AGP@QFP48 [DX3007]
M30260F8TGP@QFP48 [DX3007]
M30260F8VGP@QFP48 [DX3007]
M30262F3GP@QFP48 [DX3007]
M30262F4GP@QFP48 [DX3007]
M30262F6GP@QFP48 [DX3007]
M30262F8GP@QFP48 [DX3007]
M30263F3AFP@SSOP42 [DX1056]
M30263F6AFP@SSOP42 [DX1056]
M30263F8AFP@SSOP42 [DX1056]
M30280F6HP@QFP80 [DX3016]
M30280F8HP@QFP80 [DX3016]
M30280FAHP@QFP80 [DX3016]
M30280FATHP@QFP80 [DX3016]
M30280FAVHP@QFP80 [DX3016]
M30280FCHP@QFP80 [DX3016]
M30281F6HP@QFP64 [DX3011]
M30281F8HP@QFP64 [DX3011]
M30281FAHP@QFP64 [DX3011]
M30281FATHP@QFP64 [DX3011]
M30281FAVHP@QFP64 [DX3011]
M30281FCHP@QFP64 [DX3011]
M30290FAHP@QFP80 [DX3016]
M30290FATHP@QFP80 [DX3016]
M30290FAVHP@QFP80 [DX3016]
M30290FCHP@QFP80 [DX3016]
M30290FCTHP@QFP80 [DX3016]
M30290FCVHP@QFP80 [DX3016]
M30291F8HP@QFP64 [DX3011]
M30291F8THP@QFP64 [DX3011]
M30291F8VHP@QFP64 [DX3011]
M30291FAHP@QFP64 [DX3011]
M30291FATHP@QFP64 [DX3011]
M30291FAVHP@QFP64 [DX3011]
M30291FCHP@QFP64 [DX3011]
M30291FCTHP@QFP64 [DX3011]
M30291FCVHP@QFP64 [DX3011]
M30302FAPFP@PQFP100 [DX3045]
M30302FAPGP@QFP100 [DX3021]
M30302FCPFP@PQFP100 [DX3045]
M30302FCPGP@QFP100 [DX3021]
M30302FEPFP@PQFP100 [DX3045]
M30302FEPGP@QFP100 [DX3021]
M3030RFAPFP [DX3045]
M3030RFAPGP [DX3021]
M3030RFCPFP [DX3045]
M3030RFCPGP [DX3021]
M3030RFEPFP [DX3045]
M3030RFEPGP [DX3021]
M3030RFGPFP [DX3045]
M3030RFGPGP [DX3021]
M30620FCAFP@PQFP100 [DX3045]
M30620FCAGP@TQFP100 [DX3021]
M30620FCNFP@PQFP100 [DX3045]
M30620FCNGP@TQFP100 [DX3021]
M30620FCPFP@PQFP100 [DX3045]
M30620FCPFP@PQFP100(S) [DX3045]
M30620FCPGP@TQFP100 [DX3021]
M30620FCPGP@TQFP100(S) [DX3021]
M30621FCPGP@TQFP100(S) [DX3018]
M30622F8PFP@PQFP100 [DX3045]
M30622F8PFP@PQFP100(S) [DX3045]

M30622F8PGP@TQFP100 [DX3021]
M30622F8PGP@TQFP100(S) [DX3021]
M30624FGAFP@PQFP100 [DX3045]
M30624FGAGP@TQFP100 [DX3021]
M30624FGMFP@PQFP100 [DX3045]
M30624FGMGP@TQFP100 [DX3021]
M30624FGNFP@PQFP100 [DX3045]
M30624FGNGP@TQFP100 [DX3021]
M30624FGPFP@PQFP100 [DX3045]
M30624FGPFP@PQFP100(S) [DX3045]
M30624FGPGP@TQFP100 [DX3021]
M30624FGPGP@TQFP100(S) [DX3021]
M30625FGPGP@TQFP128 [DX3032]
M30625FGPGP@TQFP128(S) [DX3032]
M30626FHPFP@PQFP100 [DX3045]
M30626FHPFP@PQFP100(S) [DX3045]
M30626FHPGP@TQFP100 [DX3021]
M30626FHPGP@TQFP100(S) [DX3021]
M30626FJPFP@PQFP100 [DX3045]
M30626FJPFP@PQFP100(S) [DX3045]
M30626FJPGP@PQFP100 [DX3021]
M30626FJPGP@PQFP100(S) [DX3021]
M30627FHPGP@PQFP128 [DX3032]
M30627FHPGP@PQFP128(S) [DX3032]
M30627FJPGP@PQFP128 [DX3032]
M30627FJPGP@PQFP128(S) [DX3032]
M3062AFCTFP@PQFP100 [DX3045]
M3062AFCTFP@PQFP100(S) [DX3045]
M3062AFCTGP@PQFP100 [DX3021]
M3062AFCTGP@PQFP100(S) [DX3021]
M3062AFCVFP@PQFP100 [DX3045]
M3062AFCVFP@PQFP100(S) [DX3045]
M3062AFCVGP@PQFP100 [DX3021]
M3062AFCVGP@PQFP100(S) [DX3021]
M3062CF8TFP@PQFP100 [DX3045]
M3062CF8TFP@PQFP100(S) [DX3045]
M3062CF8TGP@PQFP100 [DX3021]
M3062CF8TGP@PQFP100(S) [DX3021]
M3062JFHTFP@PQFP100 [DX3045]
M3062JFHTFP@PQFP100(S) [DX3045]
M3062JFHTGP@PQFP100 [DX3021]
M3062JFHTGP@PQFP100(S) [DX3021]
M3062JFHVFP@PQFP100 [DX3045]
M3062JFHVFP@PQFP100(S) [DX3045]
M3062JFHVGP@PQFP100 [DX3021]
M3062JFHVGP@PQFP100(S) [DX3021]
M3062LFGPFP@PQFP100 [DX3045]
M3062LFGPFP@PQFP100(S) [DX3045]
M3062LFGPGP@TQFP100 [DX3021]
M3062LFGPGP@TQFP100(S) [DX3021]
M306N4FCFP@PQFP100 [DX3045]
M306N4FCGP@QFP100 [DX3021]
M306N4FCTFP@PQFP100 [DX3045]
M306N4FCTGP@QFP100 [DX3021]
M306N4FCVFP@PQFP100 [DX3045]
M306N4FCVGP@QFP100 [DX3021]
M306N4FGFP@PQFP100 [DX3045]
M306N4FGGP@QFP100 [DX3021]
M306N4FGTFP@PQFP100 [DX3045]
M306N4FGTGP@QFP100 [DX3021]
M306N4FGVFP@PQFP100 [DX3045]
M306N4FGVGP@QFP100 [DX3021]
M306N5FCFP@PQFP100 [DX3045]
M306N5FCGP@QFP100 [DX3021]
M306N5FCTFP@PQFP100 [DX3045]
M306N5FCTGP@QFP100 [DX3021]
M306N5FCVFP@PQFP100 [DX3045]
M306N5FCVGP@QFP100 [DX3021]
M306NAFGTFP@PQFP100 [DX3045]
M306NBFCTFP@PQFP100 [DX3045]
M306NKFHGP@QFP100 [DX3021]
M306NKFHTGP@QFP100 [DX3021]
M306NKFHVGP@QFP100 [DX3021]
M306NKFJGP@QFP100 [DX3021]
M306NKFJTGP@QFP100 [DX3021]
M306NKFJVGP@QFP100 [DX3021]
M306NLFHGP@QFP100 [DX3021]
M306NLFHTGP@QFP100 [DX3021]
M306NLFHVGP@QFP100 [DX3021]
M306NLFJGP@QFP100 [DX3021]
M306NLFJTGP@QFP100 [DX3021]
M306NLFJVGP@QFP100 [DX3021]
M306NMFHGP@QFP128 [DX3032]
M306NMFHTGP@QFP128 [DX3032]
M306NMFHVGP@QFP128 [DX3032]
M306NMFJGP@QFP128 [DX3032]
M306NMFJTGP@QFP128 [DX3032]
M306NMFJVGP@QFP128 [DX3032]
M306NNFHGP@QFP128 [DX3032]
M306NNFHTGP@QFP128 [DX3032]
M306NNFHVGP@QFP128 [DX3032]
M306NNFJGP@QFP128 [DX3032]
M306NNFJTGP@QFP128 [DX3032]
M306NNFJVGP@QFP128 [DX3032]
M30833FJFP@PQFP100 [DX3045]
M30833FJGP@TQFP100 [DX3021]

M30833FJTGP@TQFP100 [DX3021]
M30835FJGP@QFP144 [DX3035]
M30873FHGP@TQFP100 [DX3021]
M30875FHGP@TQFP144 [DX3035]
M30876FJGP@TQFP100 [DX3021]
M30878FJGP@TQFP144 [DX3035]
M30879FKGP@TQFP100 [DX3021]
M30879FLFP@TQFP100 [DX3045]
M30879FLGP@TQFP100 [DX3021]
M3087BFKGP@TQFP144 [DX3035]
M3087BFLGP@TQFP144 [DX3035]
M34282E2GP [DX1000]
M34283G2GP [DX1067]
M34286G2GP [DX1067]
M34508G4FP [DX1031]
M34508G4GP [DX1067]
M34508G4HFP [DX1031]
M34508G4HGP [DX1067]
M34509G4FP [DX1047]
M34509G4HFP [DX1047]
M34559G6FP@QFP52 [DX3010]
M3455AG8FP@QFP52 [DX3010]
M3455AGCFP@QFP52 [DX3010]
M37531E4FP@SSOP36 [DX1056]
M37531E8FP@SSOP36 [DX1056]
M37544G2(GP)@LQFP32 [DX3001]
M37544G2(SP)@SDIP32 [DX0032]
M37544G2A(GP)@LQFP32 [DX3001]
M37544G2A(SP)@SDIP32 [DX0032]
M37545G4(FP)@SSOP36 [DX1046]
M37545G4(GP)@LQFP32 [DX3001]
M37545G6(FP)@SSOP36 [DX1046]
M37545G6(GP)@LQFP32 [DX3001]
M37545G8(FP)@SSOP36 [DX1046]
M37545G8(GP)@LQFP32 [DX3001]
M37546G2(FP)@SSOP36 [DX1046]
M37546G2(GP)@LQFP32 [DX3001]
M37546G2(SP)@SDIP32 [DX0032]
M37546G4(FP)@SSOP36 [DX1046]
M37546G4(GP)@LQFP32 [DX3001]
M37546G4(SP)@SDIP32 [DX0032]
M37547G2(FP)@SSOP36 [DX1046]
M37547G4(FP)@SSOP36 [DX1046]
M37548G1(FP)@TSSOP20 [DX1000]
M37548G2(FP)@TSSOP20 [DX1000]
M37548G3(FP)@TSSOP20 [DX1000]
M37549G1FP@SSOP24 [DX1047]
M37549G1SP@SDIP24 [DX0032]
M37549G2FP@SSOP24 [DX1047]
M37549G2SP@SDIP24 [DX0032]
M37549G3FP@SSOP24 [DX1047]
M37549G3SP@SDIP24 [DX0032]
M38039FFFP@QFP64 [DX3044]
M38039FFHFP@QFP64 [DX3044]
M38039FFHHP@QFP64 [DX3011]
M38039FFHKP@QFP64 [DX3044]
M38039FFHP@QFP64 [DX3011]
M38039FFHSP@SDIP64 [DX0064]
M38039FFSP@SDIP64 [DX0064]
M38039G4HHP@QFP64 [DX3011]
M38039G4HKP@QFP64 [DX3013]
M38039G4HSP@SDIP64 [DX0064]
M38039G6HHP@QFP64 [DX3011]
M38039G6HKP@QFP64 [DX3013]
M38039G6HSP@SDIP64 [DX0064]
M38039G8HHP@QFP64 [DX3011]
M38039G8HKP@QFP64 [DX3013]
M38039G8HSP@SDIP64 [DX0064]
M38039GCHHP@QFP64 [DX3011]
M38039GCHKP@QFP64 [DX3013]
M38039GCHSP@SDIP64 [DX0064]
M38049FFFP@QFP64 [DX3044]
M38049FFHP@QFP64 [DX3011]
M38049FFSP@SDIP64 [DX0064]
M38234G4(FP)@PQFP80 [DX3020]
M38234G4(HP)@TQFP80 [DX3016]
M38235G6(FP)@PQFP80 [DX3020]
M38235G6(HP)@TQFP80 [DX3016]
M38238G8(FP)@PQFP80 [DX3020]
M38238G8(HP)@TQFP80 [DX3016]
M38239GC(FP)@PQFP80 [DX3020]
M38239GC(HP)@TQFP80 [DX3016]
M3823AGF(FP)@PQFP80 [DX3020]
M3823AGF(HP)@TQFP80 [DX3016]
M38503G4A(FP)@SSOP42 [DX1046]
M38503G4A(SP)@SDIP42 [DX0042]
M38507F8FP@SSOP42 [DX1056]
M38507F8SP@SDIP42 [DX0042]
M38588G6(FP)@SSOP42 [DX1046]
M38588G6(SP)@SDIP42 [DX0042]
M38588G8(FP)@SSOP42 [DX1046]
M38588G8(SP)@SDIP42 [DX0042]
M38588GC(FP)@SSOP42 [DX1046]
M38588GC(SP)@SDIP42 [DX0042]
M38859FFHP@QFP80 [DX3016]
M38D24G4(FP)@QFP64 [DX3013]

M38D24G4(HP)@QFP64 [DX3011]
M38D24G6(HP)@QFP64 [DX3011]
M38D28G8(HP)@QFP64 [DX3011]
M38D29GC(FP)@QFP64 [DX3013]
M38D29GF(FP)@QFP64 [DX3013]
M38D58G8FP@PQFP80 [DX3020]
M38D59FFFP@PQFP80 [DX3020]
M38D59GCFP@PQFP80 [DX3020]
M38D59GFFP@PQFP80 [DX3020]
M3NN00FETGP@QFP100 [DX3021]
R4F20102DFA [DX3011-3]
R4F20102NFA [DX3011-3]
R4F20102RDFA [DX3011-3]
R4F20102RNFA [DX3011-3]
R4F20103DFA [DX3011-3]
R4F20103NFA [DX3011-3]
R4F20103RDFA [DX3011-3]
R4F20103RNFA [DX3011-3]
R4F20114DFA [DX3011-3]
R4F20114NFA [DX3011-3]
R4F20114RDFA [DX3011-3]
R4F20114RNFA [DX3011-3]
R4F20115DFA [DX3011-3]
R4F20115NFA [DX3011-3]
R4F20115RDFA [DX3011-3]
R4F20115RNFA [DX3011-3]
R4F20202DFC [DX3016-1]
R4F20202NFC [DX3016-1]
R4F20202RDFC [DX3016-1]
R4F20202RNFC [DX3016-1]
R4F20203DFC [DX3016-1]
R4F20203NFC [DX3016-1]
R4F20203RDFC [DX3016-1]
R4F20203RNFC [DX3016-1]
R4F20214DFC [DX3016-1]
R4F20214NFC [DX3016-1]
R4F20214RDFC [DX3016-1]
R4F20214RNFC [DX3016-1]
R4F20215DFC [DX3016-1]
R4F20215NFC [DX3016-1]
R4F20215RDFC [DX3016-1]
R4F20215RNFC [DX3016-1]
R4F20222DFC [DX3016-1]
R4F20222NFC [DX3016-1]
R4F20222RDFC [DX3016-1]
R4F20222RNFC [DX3016-1]
R4F20223DFC [DX3016-1]
R4F20223NFC [DX3016-1]
M38D24G6(FP)@QFP64 [DX3013]
M38D28G8(FP)@QFP64 [DX3013]
M38D29FF(HP)@QFP64 [DX3011]
M38D29GC(HP)@QFP64 [DX3011]
M38D29GF(HP)@QFP64 [DX3011]
M38D58G8HP@QFP80 [DX3016]
M38D59FFHP@QFP80 [DX3016]
M38D59GCHP@QFP80 [DX3016]
M38D59GFHP@QFP80 [DX3016]
M3NN00FETGP@QFP100(S) [DX3021]
R4F20102DFB [DX3014-1]
R4F20102NFB [DX3014-1]
R4F20102RDFB [DX3014-1]
R4F20102RNFB [DX3014-1]
R4F20103DFB [DX3014-1]
R4F20103NFB [DX3014-1]
R4F20103RDFB [DX3014-1]
R4F20103RNFB [DX3014-1]
R4F20114DFB [DX3014-1]
R4F20114NFB [DX3014-1]
R4F20114RDFB [DX3014-1]
R4F20114RNFB [DX3014-1]
R4F20115DFB [DX3014-1]
R4F20115NFB [DX3014-1]
R4F20115RDFB [DX3014-1]
R4F20115RNFB [DX3014-1]
R4F20202DFD [DX3018-1]
R4F20202NFD [DX3018-1]
R4F20202RDFD [DX3018-1]
R4F20202RNFD [DX3018-1]
R4F20203DFD [DX3018-1]
R4F20203NFD [DX3018-1]
R4F20203RDFD [DX3018-1]
R4F20203RNFD [DX3018-1]
R4F20214DFD [DX3018-1]
R4F20214NFD [DX3018-1]
R4F20214RDFD [DX3018-1]
R4F20214RNFD [DX3018-1]
R4F20215DFD [DX3018-1]
R4F20215NFD [DX3018-1]
R4F20215RDFD [DX3018-1]
R4F20215RNFD [DX3018-1]
R4F20222DFD [DX3018-1]
R4F20222NFD [DX3018-1]
R4F20222RDFD [DX3018-1]
R4F20222RNFD [DX3018-1]
R4F20223DFD [DX3018-1]
R4F20223NFD [DX3018-1]

R4F20223RDFC [DX3016-1]
R4F20223RNFC [DX3016-1]
R4F20234DFC [DX3016-1]
R4F20234NFC [DX3016-1]
R4F20234RDFC [DX3016-1]
R4F20234RNFC [DX3016-1]
R4F20235DFC [DX3016-1]
R4F20235NFC [DX3016-1]
R4F20235RDFC [DX3016-1]
R4F20235RNFC [DX3016-1]
R4F20322RDFE [DX3021-2]
R4F20323RDFE [DX3021-2]
R4F20334RDFE [DX3021-2]
R4F20335RDFE [DX3021-2]
R4F2112BG25@FBGA176 [DX5163]
R4F2112RTE25@TQFP144 [DX3034]
R4F2112RVTE25@TQFP144 [DX3034]
R4F2112VBG25@FBGA176 [DX5163]
R4F2113NFT@QFP144 [DX3034]
R4F2116RBG20@FBGA176 [DX5163]
R4F2116RVBG20@FBGA176 [DX5163]
R4F2116TE20@QFP144 [DX3034]
R4F2116VTE20@QFP144 [DX3034]
R4F2117RBG20@FBGA176 [DX5163]
R4F2117RVBG20@FBGA176 [DX5163]
R4F2117TE20@TQFP144 [DX3034]
R4F2117VTE20@TQFP144 [DX3034]
R4F24245DFPV [DX3027]
R4F24245DVFPV [DX3027]
R4F24245NFPV [DX3027]
R4F24245NVFPV [DX3027]
R4F24248DFPV [DX3027]
R4F24248DVFPV [DX3027]
R4F24248NFPV [DX3027]
R4F24248NVFPV [DX3027]
R4F24249DFPV [DX3027]
R4F24249DVFPV [DX3027]
R4F24249NFPV [DX3027]
R4F24249NVFPV [DX3027]
R4F24255DFPU [DX3027]
R4F24255DVFPU [DX3027]
R4F24255NFPU [DX3027]
R4F24255NVFPU [DX3027]
R4F24256DFPU [DX3027]
R4F24256DVFPU [DX3027]
R4F24256NFPU [DX3027]
R4F24256NVFPU [DX3027]
R4F24258DFPU [DX3027]
R4F20223RDFD [DX3018-1]
R4F20223RNFD [DX3018-1]
R4F20234DFD [DX3018-1]
R4F20234NFD [DX3018-1]
R4F20234RDFD [DX3018-1]
R4F20234RNFD [DX3018-1]
R4F20235DFD [DX3018-1]
R4F20235NFD [DX3018-1]
R4F20235RDFD [DX3018-1]
R4F20235RNFD [DX3018-1]
R4F20322RNFE [DX3021-2]
R4F20323RNFE [DX3021-2]
R4F20334RNFE [DX3021-2]
R4F20335RNFE [DX3021-2]
R4F2112RBG25@FBGA176 [DX5163]
R4F2112RVBG25@FBGA176 [DX5163]
R4F2112TE25@TQFP144 [DX3034]
R4F2112VTE25@TQFP144 [DX3034]
R4F2116BG20@FBGA176 [DX5163]
R4F2116RTE20@QFP144 [DX3034]
R4F2116RVTE20@QFP144 [DX3034]
R4F2116VBG20@FBGA176 [DX5163]
R4F2117BG20@FBGA176 [DX5163]
R4F2117RTE20@TQFP144 [DX3034]
R4F2117RVTE20@TQFP144 [DX3034]
R4F2117VBG20@FBGA176 [DX5163]
R4F24245DFAU [DX3028]
R4F24245DVFAU [DX3028]
R4F24245NFAU [DX3028]
R4F24245NVFAU [DX3028]
R4F24248DFAU [DX3028]
R4F24248DVFAU [DX3028]
R4F24248NFAU [DX3028]
R4F24248NVFAU [DX3028]
R4F24249DFAU [DX3028]
R4F24249DVFAU [DX3028]
R4F24249NFAU [DX3028]
R4F24249NVFAU [DX3028]
R4F24255DFAU [DX3028]
R4F24255DVFAU [DX3028]
R4F24255NFAU [DX3028]
R4F24255NVFAU [DX3028]
R4F24256DFAU [DX3028]
R4F24256DVFAU [DX3028]
R4F24256NFAU [DX3028]
R4F24256NVFAU [DX3028]
R4F24258DFAU [DX3028]
R4F24258DVFAU [DX3028]

R4F24258DVFPU [DX3027]
R4F24258NFPU [DX3027]
R4F24258NVFPU [DX3027]
R4F24259DFPU [DX3027]
R4F24259DVFPU [DX3027]
R4F24259NFPU [DX3027]
R4F24259NVFPU [DX3027]
R4F24265DVFQV [DX3051]
R4F24265NFQV [DX3051]
R4F24265NVRFQV [DX3051]
R4F24268DVFQV [DX3051]
R4F24268NFQV [DX3051]
R4F24268NVRFQV [DX3051]
R4F24269DVFQV [DX3051]
R4F24269NFQV [DX3051]
R4F24269NVRFQV [DX3051]
R4F24275DVFQU [DX3051]
R4F24275NFQU [DX3051]
R4F24275NVRFQU [DX3051]
R4F24276DVFQU [DX3051]
R4F24276NFQU [DX3051]
R4F24276NVRFQU [DX3051]
R4F24278DVFQU [DX3051]
R4F24278NFQU [DX3051]
R4F24278NVRFQU [DX3051]
R4F24279DVFQU [DX3051]
R4F24279NFQU [DX3051]
R4F24279NVRFQU [DX3051]
R4F24545DVFPV [DX3027]
R4F24545NVFPV [DX3027]
R4F24548DVFPV [DX3027]
R4F24548NVFPV [DX3027]
R4F24549DVFPV [DX3027]
R4F24549NVFPV [DX3027]
R4F24565DVRFQV [DX3051]
R4F24565NVRFQV [DX3051]
R4F24568DVRFQV [DX3051]
R4F24568NVRFQV [DX3051]
R4F24569DVRFQV [DX3051]
R4F24569NVRFQV [DX3051]
R4F2463VTE34V@TQFP144 [DX3034]
R5F1006ADSP [DX1026]
R5F1006CDSP [DX1026]
R5F1006DDSP [DX1026]
R5F1006EDSP [DX1026]
R5F1006FDSP [DX1026]
R5F1006GDSP [DX1026]
R5F1006HDSP [DX1026]
R4F24258NFAU [DX3028]
R4F24258NVFAU [DX3028]
R4F24259DFAU [DX3028]
R4F24259DVFAU [DX3028]
R4F24259NFAU [DX3028]
R4F24259NVFAU [DX3028]
R4F24265DFQV [DX3051]
R4F24265DVRFQV [DX3051]
R4F24265NVFQV [DX3051]
R4F24268DFQV [DX3051]
R4F24268DVRFQV [DX3051]
R4F24268NVFQV [DX3051]
R4F24269DFQV [DX3051]
R4F24269DVRFQV [DX3051]
R4F24269NVFQV [DX3051]
R4F24275DFQU [DX3051]
R4F24275DVRFQU [DX3051]
R4F24275NVFQU [DX3051]
R4F24276DFQU [DX3051]
R4F24276DVRFQU [DX3051]
R4F24276NVFQU [DX3051]
R4F24278DFQU [DX3051]
R4F24278DVRFQU [DX3051]
R4F24278NVFQU [DX3051]
R4F24279DFQU [DX3051]
R4F24279DVRFQU [DX3051]
R4F24279NVFQU [DX3051]
R4F24545DVFAU [DX3028]
R4F24545NVFAU [DX3028]
R4F24548DVFAU [DX3028]
R4F24548NVFAU [DX3028]
R4F24549DVFAU [DX3028]
R4F24549NVFAU [DX3028]
R4F24565DVFQV [DX3051]
R4F24565NVFQV [DX3051]
R4F24568DVFQV [DX3051]
R4F24568NVFQV [DX3051]
R4F24569DVFQV [DX3051]
R4F24569NVFQV [DX3051]
R4F2463VTE34DV@TQFP144 [DX3034]
R5F1006AASP [DX1026]
R5F1006CASP [DX1026]
R5F1006DASP [DX1026]
R5F1006EASP [DX1026]
R5F1006FASP [DX1026]
R5F1006GASP [DX1026]
R5F1006HASP [DX1026]
R5F1006JASP [DX1026]

R5F1006JDSP [DX1026]
R5F1006KDSP [DX1026]
R5F1006LDSP [DX1026]
R5F1007ADNA [DX4012]
R5F1007CDNA [DX4012]
R5F1007DDNA [DX4012]
R5F1007EDNA [DX4012]
R5F1007FDNA [DX4012]
R5F1007GDNA [DX4012]
R5F1007HDNA [DX4012]
R5F1007JDNA [DX4012]
R5F1007KDNA [DX4012]
R5F1007LDNA [DX4012]
R5F1008ADLA [DX0001]
R5F1008CDLA [DX0001]
R5F1008DDLA [DX0001]
R5F1008EDLA [DX0001]
R5F1008FDLA [DX0001]
R5F1008GDLA [DX0001]
R5F1008HDLA [DX0001]
R5F1008JDLA [DX0001]
R5F1008KDLA [DX0001]
R5F1008LDLA [DX0001]
R5F100AADSP [DX1027]
R5F100ACDSP [DX1027]
R5F100ADDSP [DX1027]
R5F100AEDSP [DX1027]
R5F100AFDSP [DX1027]
R5F100AGDSP [DX1027]
R5F100AHDSP [DX1027]
R5F100AJDSP [DX1027]
R5F100AKDSP [DX1027]
R5F100ALDSP [DX1027]
R5F100BADNA [DX4015]
R5F100BCDNA [DX4015]
R5F100BDDNA [DX4015]
R5F100BEDNA [DX4015]
R5F100BFDNA [DX4015]
R5F100BGDNA [DX4015]
R5F100BHDNA [DX4015]
R5F100BJDNA [DX4015]
R5F100BKDNA [DX4015]
R5F100BLDNA [DX4015]
R5F100CADLA [DX0001]
R5F100CCDLA [DX0001]
R5F100CDDLA [DX0001]
R5F100CEDLA [DX0001]
R5F100CFDLA [DX0001]
R5F1006KASP [DX1026]
R5F1006LASP [DX1026]
R5F1007AANA [DX4012]
R5F1007CANA [DX4012]
R5F1007DANA [DX4012]
R5F1007EANA [DX4012]
R5F1007FANA [DX4012]
R5F1007GANA [DX4012]
R5F1007HANA [DX4012]
R5F1007JANA [DX4012]
R5F1007KANA [DX4012]
R5F1007LANA [DX4012]
R5F1008AALA [DX0001]
R5F1008CALA [DX0001]
R5F1008DALA [DX0001]
R5F1008EALA [DX0001]
R5F1008FALA [DX0001]
R5F1008GALA [DX0001]
R5F1008HALA [DX0001]
R5F1008JALA [DX0001]
R5F1008KALA [DX0001]
R5F1008LALA [DX0001]
R5F100AAASP [DX1027]
R5F100ACASP [DX1027]
R5F100ADASP [DX1027]
R5F100AEASP [DX1027]
R5F100AFASP [DX1027]
R5F100AGASP [DX1027]
R5F100AHASP [DX1027]
R5F100AJASP [DX1027]
R5F100AKASP [DX1027]
R5F100ALASP [DX1027]
R5F100BAANA [DX4015]
R5F100BCANA [DX4015]
R5F100BDANA [DX4015]
R5F100BEANA [DX4015]
R5F100BFANA [DX4015]
R5F100BGANA [DX4015]
R5F100BHANA [DX4015]
R5F100BJANA [DX4015]
R5F100BKANA [DX4015]
R5F100BLANA [DX4015]
R5F100CAALA [DX0001]
R5F100CCALA [DX0001]
R5F100CDALA [DX0001]
R5F100CEALA [DX0001]
R5F100CFALA [DX0001]
R5F100CGALA [DX0001]

R5F100CGDLA [DX0001]
R5F100CHDLA [DX0001]
R5F100CJDLA [DX0001]
R5F100CKDLA [DX0001]
R5F100CLDLA [DX0001]
R5F100EADNA [DX4017]
R5F100ECDNA [DX4017]
R5F100EDDNA [DX4017]
R5F100EEDNA [DX4017]
R5F100EFDNA [DX4017]
R5F100EGDNA [DX4017]
R5F100EHDNA [DX4017]
R5F100EJDNA [DX4017]
R5F100EKDNA [DX4017]
R5F100ELDNA [DX4017]
R5F100FADFP [DX3005]
R5F100FCDFP [DX3005]
R5F100FDDFP [DX3005]
R5F100FEDFP [DX3005]
R5F100FFDFP [DX3005]
R5F100FGDFP [DX3005]
R5F100FHDFP [DX3005]
R5F100FJDFP [DX3005]
R5F100FKDFP [DX3005]
R5F100FLDFP [DX3005]
R5F100GAANA [DX4021]
R5F100GADNA [DX4021]
R5F100GCANA [DX4021]
R5F100GCDNA [DX4021]
R5F100GDANA [DX4021]
R5F100GDDNA [DX4021]
R5F100GEANA [DX4021]
R5F100GEDNA [DX4021]
R5F100GFANA [DX4021]
R5F100GFDNA [DX4021]
R5F100GGANA [DX4021]
R5F100GGDNA [DX4021]
R5F100GHANA [DX4021]
R5F100GHDNA [DX4021]
R5F100GJANA [DX4021]
R5F100GJDNA [DX4021]
R5F100GKANA [DX4021]
R5F100GKDNA [DX4021]
R5F100GLANA [DX4021]
R5F100GLDNA [DX4021]
R5F100JCDFA [DX3010]
R5F100JDDFA [DX3010]
R5F100JEDFA [DX3010]
R5F100CHALA [DX0001]
R5F100CJALA [DX0001]
R5F100CKALA [DX0001]
R5F100CLALA [DX0001]
R5F100EAANA [DX4017]
R5F100ECANA [DX4017]
R5F100EDANA [DX4017]
R5F100EEANA [DX4017]
R5F100EFANA [DX4017]
R5F100EGANA [DX4017]
R5F100EHANA [DX4017]
R5F100EJANA [DX4017]
R5F100EKANA [DX4017]
R5F100ELANA [DX4017]
R5F100FAAFP [DX3005]
R5F100FCAFP [DX3005]
R5F100FDAFP [DX3005]
R5F100FEAFP [DX3005]
R5F100FFAFP [DX3005]
R5F100FGAFP [DX3005]
R5F100FHAFP [DX3005]
R5F100FJAFP [DX3005]
R5F100FKAFP [DX3005]
R5F100FLAFP [DX3005]
R5F100GAAFB [DX3007]
R5F100GADFB [DX3007]
R5F100GCAFB [DX3007]
R5F100GCDFB [DX3007]
R5F100GDAFB [DX3007]
R5F100GDDFB [DX3007]
R5F100GEAFB [DX3007]
R5F100GEDFB [DX3007]
R5F100GFAFB [DX3007]
R5F100GFDFB [DX3007]
R5F100GGAFB [DX3007]
R5F100GGDFB [DX3007]
R5F100GHAFB [DX3007]
R5F100GHDFB [DX3007]
R5F100GJAFB [DX3007]
R5F100GJDFB [DX3007]
R5F100GKAFB [DX3007]
R5F100GKDFB [DX3007]
R5F100GLAFB [DX3007]
R5F100GLDFB [DX3007]
R5F100JCAFA [DX3010]
R5F100JDAFA [DX3010]
R5F100JEAFA [DX3010]
R5F100JFAFA [DX3010]

R5F100JFDFA [DX3010]
R5F100JGAFA [DX3010]
R5F100JGDFA [DX3010]
R5F100JHAFA [DX3010]
R5F100JHDFA [DX3010]
R5F100JJAFA [DX3010]
R5F100JJDFA [DX3010]
R5F100JKAFA [DX3010]
R5F100JKDFA [DX3010]
R5F100JLAFA [DX3010]
R5F100JLDFA [DX3010]
R5F100LCABG [DX0001]
R5F100LCAFA [DX3012]
R5F100LCAFB [DX3011]
R5F100LCAFC [DX3085]
R5F100LCDBG [DX0001]
R5F100LCDFA [DX3012]
R5F100LCDFB [DX3011]
R5F100LCDFC [DX3085]
R5F100LDABG [DX0001]
R5F100LDAFA [DX3012]
R5F100LDAFB [DX3011]
R5F100LDAFC [DX3085]
R5F100LDDBG [DX0001]
R5F100LDDFA [DX3012]
R5F100LDDFB [DX3011]
R5F100LDDFC [DX3085]
R5F100LEABG [DX0001]
R5F100LEAFA [DX3012]
R5F100LEAFB [DX3011]
R5F100LEAFC [DX3085]
R5F100LEDBG [DX0001]
R5F100LEDFA [DX3012]
R5F100LEDFB [DX3011]
R5F100LEDFC [DX3085]
R5F100LFABG [DX0001]
R5F100LFAFA [DX3012]
R5F100LFAFB [DX3011]
R5F100LFAFC [DX3085]
R5F100LFDBG [DX0001]
R5F100LFDFA [DX3012]
R5F100LFDFB [DX3011]
R5F100LFDFC [DX3085]
R5F100LGABG [DX0001]
R5F100LGAFA [DX3012]
R5F100LGAFB [DX3011]
R5F100LGAFC [DX3085]
R5F100LGDBG [DX0001]
R5F100LGDFA [DX3012]
R5F100LGDFB [DX3011]
R5F100LGDFC [DX3085]
R5F100LHABG [DX0001]
R5F100LHAFA [DX3012]
R5F100LHAFB [DX3011]
R5F100LHAFC [DX3085]
R5F100LHDBG [DX0001]
R5F100LHDFA [DX3012]
R5F100LHDFB [DX3011]
R5F100LHDFC [DX3085]
R5F100LJABG [DX0001]
R5F100LJAFA [DX3012]
R5F100LJAFB [DX3011]
R5F100LJAFC [DX3085]
R5F100LJDBG [DX0001]
R5F100LJDFA [DX3012]
R5F100LJDFB [DX3011]
R5F100LJDFC [DX3085]
R5F100LKABG [DX0001]
R5F100LKAFA [DX3012]
R5F100LKAFB [DX3011]
R5F100LKAFC [DX3085]
R5F100LKDBG [DX0001]
R5F100LKDFA [DX3012]
R5F100LKDFB [DX3011]
R5F100LKDFC [DX3085]
R5F100LLABG [DX0001]
R5F100LLAFA [DX3012]
R5F100LLAFB [DX3011]
R5F100LLAFC [DX3085]
R5F100LLDBG [DX0001]
R5F100LLDFA [DX3012]
R5F100LLDFB [DX3011]
R5F100LLDFC [DX3085]
R5F100MCAFA [DX3017]
R5F100MCAFB [DX3016]
R5F100MCDFA [DX3017]
R5F100MCDFB [DX3016]
R5F100MDAFA [DX3017]
R5F100MDAFB [DX3016]
R5F100MDDFA [DX3017]
R5F100MDDFB [DX3016]
R5F100MEAFA [DX3017]
R5F100MEAFB [DX3016]
R5F100MEDFA [DX3017]
R5F100MEDFB [DX3016]
R5F100MFAFA [DX3017]

R5F100MFAFB [DX3016]
R5F100MFDFB [DX3016]
R5F100MGAFB [DX3016]
R5F100MGDFB [DX3016]
R5F100MHAFB [DX3016]
R5F100MHDFB [DX3016]
R5F100MJAFB [DX3016]
R5F100MJDFB [DX3016]
R5F100MKAFB [DX3016]
R5F100MKDFB [DX3016]
R5F100MLAFB [DX3016]
R5F100MLDFB [DX3016]
R5F100PCAFB [DX3021]
R5F100PCDFB [DX3021]
R5F100PDAFB [DX3021]
R5F100PDDFB [DX3021]
R5F100PEAFB [DX3021]
R5F100PEDFB [DX3021]
R5F100PFAFB [DX3021]
R5F100PFDFB [DX3021]
R5F100PGAFB [DX3021]
R5F100PGDFB [DX3021]
R5F100PHAFB [DX3021]
R5F100PHDFB [DX3021]
R5F100PJAFB [DX3021]
R5F100PJDFB [DX3021]
R5F100PKAFB [DX3021]
R5F100PKDFB [DX3021]
R5F100PLAFB [DX3021]
R5F100PLDFB [DX3021]
R5F100SCDFB [DX3031]
R5F100SDDFB [DX3031]
R5F100SEDFB [DX3031]
R5F100SFDFB [DX3031]
R5F100SGDFB [DX3031]
R5F100SHDFB [DX3031]
R5F100SJDFB [DX3031]
R5F100SKDFB [DX3031]
R5F100SLDFB [DX3031]
R5F1016ADSP [DX1026]
R5F1016CDSP [DX1026]
R5F1016DDSP [DX1026]
R5F1016EDSP [DX1026]
R5F1016FDSP [DX1026]
R5F1016GDSP [DX1026]
R5F1016HDSP [DX1026]
R5F1016JDSP [DX1026]
R5F1016KDSP [DX1026]
R5F100MFDFA [DX3017]
R5F100MGAFA [DX3017]
R5F100MGDFA [DX3017]
R5F100MHAFA [DX3017]
R5F100MHDFA [DX3017]
R5F100MJAFA [DX3017]
R5F100MJDFA [DX3017]
R5F100MKAFA [DX3017]
R5F100MKDFA [DX3017]
R5F100MLAFA [DX3017]
R5F100MLDFA [DX3017]
R5F100PCAFA [DX3062]
R5F100PCDFA [DX3062]
R5F100PDAFA [DX3062]
R5F100PDDFA [DX3062]
R5F100PEAFA [DX3062]
R5F100PEDFA [DX3062]
R5F100PFAFA [DX3062]
R5F100PFDFA [DX3062]
R5F100PGAFA [DX3062]
R5F100PGDFA [DX3062]
R5F100PHAFA [DX3062]
R5F100PHDFA [DX3062]
R5F100PJAFA [DX3062]
R5F100PJDFA [DX3062]
R5F100PKAFA [DX3062]
R5F100PKDFA [DX3062]
R5F100PLAFA [DX3062]
R5F100PLDFA [DX3062]
R5F100SCAFB [DX3031]
R5F100SDAFB [DX3031]
R5F100SEAFB [DX3031]
R5F100SFAFB [DX3031]
R5F100SGAFB [DX3031]
R5F100SHAFB [DX3031]
R5F100SJAFB [DX3031]
R5F100SKAFB [DX3031]
R5F100SLAFB [DX3031]
R5F1016AASP [DX1026]
R5F1016CASP [DX1026]
R5F1016DASP [DX1026]
R5F1016EASP [DX1026]
R5F1016FASP [DX1026]
R5F1016GASP [DX1026]
R5F1016HASP [DX1026]
R5F1016JASP [DX1026]
R5F1016KASP [DX1026]
R5F1016LASP [DX1026]

R5F1016LDSP [DX1026]
R5F1017ADNA [DX4012]
R5F1017CDNA [DX4012]
R5F1017DDNA [DX4012]
R5F1017EDNA [DX4012]
R5F1017FDNA [DX4012]
R5F1017GDNA [DX4012]
R5F1017HDNA [DX4012]
R5F1017JDNA [DX4012]
R5F1017KDNA [DX4012]
R5F1017LDNA [DX4012]
R5F1018ADLA [DX0001]
R5F1018CDLA [DX0001]
R5F1018DDLA [DX0001]
R5F1018EDLA [DX0001]
R5F1018FDLA [DX0001]
R5F1018GDLA [DX0001]
R5F1018HDLA [DX0001]
R5F1018JDLA [DX0001]
R5F1018KDLA [DX0001]
R5F1018LDLA [DX0001]
R5F101AADSP [DX1027]
R5F101ACDSP [DX1027]
R5F101ADDSP [DX1027]
R5F101AEDSP [DX1027]
R5F101AFDSP [DX1027]
R5F101AGDSP [DX1027]
R5F101AHDSP [DX1027]
R5F101AJDSP [DX1027]
R5F101AKDSP [DX1027]
R5F101ALDSP [DX1027]
R5F101BADNA [DX4015]
R5F101BCDNA [DX4015]
R5F101BDDNA [DX4015]
R5F101BEDNA [DX4015]
R5F101BFDNA [DX4015]
R5F101BGDNA [DX4015]
R5F101BHDNA [DX4015]
R5F101BJDNA [DX4015]
R5F101BKDNA [DX4015]
R5F101BLDNA [DX4015]
R5F101CADLA [DX0001]
R5F101CCDLA [DX0001]
R5F101CDDLA [DX0001]
R5F101CEDLA [DX0001]
R5F101CFDLA [DX0001]
R5F101CGDLA [DX0001]
R5F101CHDLA [DX0001]
R5F1017AANA [DX4012]
R5F1017CANA [DX4012]
R5F1017DANA [DX4012]
R5F1017EANA [DX4012]
R5F1017FANA [DX4012]
R5F1017GANA [DX4012]
R5F1017HANA [DX4012]
R5F1017JANA [DX4012]
R5F1017KANA [DX4012]
R5F1017LANA [DX4012]
R5F1018AALA [DX0001]
R5F1018CALA [DX0001]
R5F1018DALA [DX0001]
R5F1018EALA [DX0001]
R5F1018FALA [DX0001]
R5F1018GALA [DX0001]
R5F1018HALA [DX0001]
R5F1018JALA [DX0001]
R5F1018KALA [DX0001]
R5F1018LALA [DX0001]
R5F101AAASP [DX1027]
R5F101ACASP [DX1027]
R5F101ADASP [DX1027]
R5F101AEASP [DX1027]
R5F101AFASP [DX1027]
R5F101AGASP [DX1027]
R5F101AHASP [DX1027]
R5F101AJASP [DX1027]
R5F101AKASP [DX1027]
R5F101ALASP [DX1027]
R5F101BAANA [DX4015]
R5F101BCANA [DX4015]
R5F101BDANA [DX4015]
R5F101BEANA [DX4015]
R5F101BFANA [DX4015]
R5F101BGANA [DX4015]
R5F101BHANA [DX4015]
R5F101BJANA [DX4015]
R5F101BKANA [DX4015]
R5F101BLANA [DX4015]
R5F101CAALA [DX0001]
R5F101CCALA [DX0001]
R5F101CDALA [DX0001]
R5F101CEALA [DX0001]
R5F101CFALA [DX0001]
R5F101CGALA [DX0001]
R5F101CHALA [DX0001]
R5F101CJALA [DX0001]

R5F101CJDLA [DX0001]
R5F101CKDLA [DX0001]
R5F101CLDLA [DX0001]
R5F101EADNA [DX4017]
R5F101ECDNA [DX4017]
R5F101EDDNA [DX4017]
R5F101EEDNA [DX4017]
R5F101EFDNA [DX4017]
R5F101EGDNA [DX4017]
R5F101EHDNA [DX4017]
R5F101EJDNA [DX4017]
R5F101EKDNA [DX4017]
R5F101ELDNA [DX4017]
R5F101FADFP [DX3005]
R5F101FCDFP [DX3005]
R5F101FDDFP [DX3005]
R5F101FEDFP [DX3005]
R5F101FFDFP [DX3005]
R5F101FGDFP [DX3005]
R5F101FHDFP [DX3005]
R5F101FJDFP [DX3005]
R5F101FKDFP [DX3005]
R5F101FLDFP [DX3005]
R5F101GAANA [DX4021]
R5F101GADNA [DX4021]
R5F101GCANA [DX4021]
R5F101GCDNA [DX4021]
R5F101GDANA [DX4021]
R5F101GDDNA [DX4021]
R5F101GEANA [DX4021]
R5F101GEDNA [DX4021]
R5F101GFANA [DX4021]
R5F101GFDNA [DX4021]
R5F101GGANA [DX4021]
R5F101GGDNA [DX4021]
R5F101GHANA [DX4021]
R5F101GHDNA [DX4021]
R5F101GJANA [DX4021]
R5F101GJDNA [DX4021]
R5F101GKANA [DX4021]
R5F101GKDNA [DX4021]
R5F101GLANA [DX4021]
R5F101GLDNA [DX4021]
R5F101JCDFA [DX3010]
R5F101JDDFA [DX3010]
R5F101JEDFA [DX3010]
R5F101JFDFA [DX3010]
R5F101JGDFA [DX3010]
R5F101CKALA [DX0001]
R5F101CLALA [DX0001]
R5F101EAANA [DX4017]
R5F101ECANA [DX4017]
R5F101EDANA [DX4017]
R5F101EEANA [DX4017]
R5F101EFANA [DX4017]
R5F101EGANA [DX4017]
R5F101EHANA [DX4017]
R5F101EJANA [DX4017]
R5F101EKANA [DX4017]
R5F101ELANA [DX4017]
R5F101FAAFP [DX3005]
R5F101FCAFP [DX3005]
R5F101FDAFP [DX3005]
R5F101FEAFP [DX3005]
R5F101FFAFP [DX3005]
R5F101FGAFP [DX3005]
R5F101FHAFP [DX3005]
R5F101FJAFP [DX3005]
R5F101FKAFP [DX3005]
R5F101FLAFP [DX3005]
R5F101GAAFB [DX3007]
R5F101GADFB [DX3007]
R5F101GCAFB [DX3007]
R5F101GCDFB [DX3007]
R5F101GDAFB [DX3007]
R5F101GDDFB [DX3007]
R5F101GEAFB [DX3007]
R5F101GEDFB [DX3007]
R5F101GFAFB [DX3007]
R5F101GFDFB [DX3007]
R5F101GGAFB [DX3007]
R5F101GGDFB [DX3007]
R5F101GHAFB [DX3007]
R5F101GHDFB [DX3007]
R5F101GJAFB [DX3007]
R5F101GJDFB [DX3007]
R5F101GKAFB [DX3007]
R5F101GKDFB [DX3007]
R5F101GLAFB [DX3007]
R5F101GLDFB [DX3007]
R5F101JCAFA [DX3010]
R5F101JDAFA [DX3010]
R5F101JEAFA [DX3010]
R5F101JFAFA [DX3010]
R5F101JGAFA [DX3010]
R5F101JHAFA [DX3010]

R5F101JHDFA [DX3010]
R5F101JJDFA [DX3010]
R5F101JKDFA [DX3010]
R5F101JLDFA [DX3010]
R5F101LCAFA [DX3012]
R5F101LCAFC [DX3085]
R5F101LCDFA [DX3012]
R5F101LCDFC [DX3085]
R5F101LDAFA [DX3012]
R5F101LDAFC [DX3085]
R5F101LDDFA [DX3012]
R5F101LDDFC [DX3085]
R5F101LEAFA [DX3012]
R5F101LEAFC [DX3085]
R5F101LEDFA [DX3012]
R5F101LEDFC [DX3085]
R5F101LFAFA [DX3012]
R5F101LFAFC [DX3085]
R5F101LFDFA [DX3012]
R5F101LFDFC [DX3085]
R5F101LGAFA [DX3012]
R5F101LGAFC [DX3085]
R5F101LGDFA [DX3012]
R5F101LGDFC [DX3085]
R5F101LHAFA [DX3012]
R5F101LHAFC [DX3085]
R5F101LHDFA [DX3012]
R5F101LHDFC [DX3085]
R5F101LJAFA [DX3012]
R5F101LJAFC [DX3085]
R5F101LJDFA [DX3012]
R5F101LJDFC [DX3085]
R5F101LKAFA [DX3012]
R5F101LKAFC [DX3085]
R5F101LKDFA [DX3012]
R5F101LKDFC [DX3085]
R5F101LLAFA [DX3012]
R5F101LLAFC [DX3085]
R5F101LLDFA [DX3012]
R5F101LLDFC [DX3085]
R5F101MCAFB [DX3016]
R5F101MCDFB [DX3016]
R5F101MDAFB [DX3016]
R5F101MDDFB [DX3016]
R5F101MEAFB [DX3016]
R5F101MEDFB [DX3016]
R5F101MFAFB [DX3016]
R5F101MFDFB [DX3016]
R5F101JJAFA [DX3010]
R5F101JKAFA [DX3010]
R5F101JLAFA [DX3010]
R5F101LCABG [DX0001]
R5F101LCAFB [DX3011]
R5F101LCDBG [DX0001]
R5F101LCDFB [DX3011]
R5F101LDABG [DX0001]
R5F101LDAFB [DX3011]
R5F101LDDBG [DX0001]
R5F101LDDFB [DX3011]
R5F101LEABG [DX0001]
R5F101LEAFB [DX3011]
R5F101LEDBG [DX0001]
R5F101LEDFB [DX3011]
R5F101LFABG [DX0001]
R5F101LFAFB [DX3011]
R5F101LFDBG [DX0001]
R5F101LFDFB [DX3011]
R5F101LGABG [DX0001]
R5F101LGAFB [DX3011]
R5F101LGDBG [DX0001]
R5F101LGDFB [DX3011]
R5F101LHABG [DX0001]
R5F101LHAFB [DX3011]
R5F101LHDBG [DX0001]
R5F101LHDFB [DX3011]
R5F101LJABG [DX0001]
R5F101LJAFB [DX3011]
R5F101LJDBG [DX0001]
R5F101LJDFB [DX3011]
R5F101LKABG [DX0001]
R5F101LKAFB [DX3011]
R5F101LKDBG [DX0001]
R5F101LKDFB [DX3011]
R5F101LLABG [DX0001]
R5F101LLAFB [DX3011]
R5F101LLDBG [DX0001]
R5F101LLDFB [DX3011]
R5F101MCAFA [DX3017]
R5F101MCDFA [DX3017]
R5F101MDAFA [DX3017]
R5F101MDDFA [DX3017]
R5F101MEAFA [DX3017]
R5F101MEDFA [DX3017]
R5F101MFAFA [DX3017]
R5F101MFDFA [DX3017]
R5F101MGAFA [DX3017]

R5F101MGAFB [DX3016]
R5F101MGDFB [DX3016]
R5F101MHAFB [DX3016]
R5F101MHDFB [DX3016]
R5F101MJAFB [DX3016]
R5F101MJDFB [DX3016]
R5F101MKAFB [DX3016]
R5F101MKDFB [DX3016]
R5F101MLAFB [DX3016]
R5F101MLDFB [DX3016]
R5F101PCAFB [DX3021]
R5F101PCDFB [DX3021]
R5F101PDAFB [DX3021]
R5F101PDDFB [DX3021]
R5F101PEAFB [DX3021]
R5F101PEDFB [DX3021]
R5F101PFAFB [DX3021]
R5F101PFDFB [DX3021]
R5F101PGAFB [DX3021]
R5F101PGDFB [DX3021]
R5F101PHAFB [DX3021]
R5F101PHDFB [DX3021]
R5F101PJAFB [DX3021]
R5F101PJDFB [DX3021]
R5F101PKAFB [DX3021]
R5F101PKDFB [DX3021]
R5F101PLAFB [DX3021]
R5F101PLDFB [DX3021]
R5F101SCDFB [DX3031]
R5F101SDDFB [DX3031]
R5F101SEDFB [DX3031]
R5F101SFDFB [DX3031]
R5F101SGDFB [DX3031]
R5F101SHDFB [DX3031]
R5F101SJDFB [DX3031]
R5F101SKDFB [DX3031]
R5F101SLDFB [DX3031]
R5F10266DSP [DX1067]
R5F10267DSP [DX1067]
R5F10268DSP [DX1067]
R5F10269DSP [DX1067]
R5F1026ADSP [DX1067]
R5F10276DNA [DX4012]
R5F10277DNA [DX4012]
R5F10278DNA [DX4012]
R5F10279DNA [DX4012]
R5F1027ADNA [DX4012]
R5F102A6DSP [DX1027]
R5F101MGDFA [DX3017]
R5F101MHAFA [DX3017]
R5F101MHDFA [DX3017]
R5F101MJAFA [DX3017]
R5F101MJDFA [DX3017]
R5F101MKAFA [DX3017]
R5F101MKDFA [DX3017]
R5F101MLAFA [DX3017]
R5F101MLDFA [DX3017]
R5F101PCAFA [DX3062]
R5F101PCDFA [DX3062]
R5F101PDAFA [DX3062]
R5F101PDDFA [DX3062]
R5F101PEAFA [DX3062]
R5F101PEDFA [DX3062]
R5F101PFAFA [DX3062]
R5F101PFDFA [DX3062]
R5F101PGAFA [DX3062]
R5F101PGDFA [DX3062]
R5F101PHAFA [DX3062]
R5F101PHDFA [DX3062]
R5F101PJAFA [DX3062]
R5F101PJDFA [DX3062]
R5F101PKAFA [DX3062]
R5F101PKDFA [DX3062]
R5F101PLAFA [DX3062]
R5F101PLDFA [DX3062]
R5F101SCAFB [DX3031]
R5F101SDAFB [DX3031]
R5F101SEAFB [DX3031]
R5F101SFAFB [DX3031]
R5F101SGAFB [DX3031]
R5F101SHAFB [DX3031]
R5F101SJAFB [DX3031]
R5F101SKAFB [DX3031]
R5F101SLAFB [DX3031]
R5F10266ASP [DX1067]
R5F10267ASP [DX1067]
R5F10268ASP [DX1067]
R5F10269ASP [DX1067]
R5F1026AASP [DX1067]
R5F10276ANA [DX4012]
R5F10277ANA [DX4012]
R5F10278ANA [DX4012]
R5F10279ANA [DX4012]
R5F1027AANA [DX4012]
R5F102A6ASP [DX1027]
R5F102A7ASP [DX1027]

R5F102A7DSP [DX1027]
R5F102A8DSP [DX1027]
R5F102A9DSP [DX1027]
R5F102AADSP [DX1027]
R5F10366DSP [DX1067]
R5F10367DSP [DX1067]
R5F10368DSP [DX1067]
R5F10369DSP [DX1067]
R5F1036ADSP [DX1067]
R5F10376DNA [DX4012]
R5F10377DNA [DX4012]
R5F10378DNA [DX4012]
R5F10379DNA [DX4012]
R5F1037ADNA [DX4012]
R5F103A6DSP [DX1027]
R5F103A7DSP [DX1027]
R5F103A8DSP [DX1027]
R5F103A9DSP [DX1027]
R5F103AADSP [DX1027]
R5F104AADSP [DX1026]
R5F104ACDSP [DX1026]
R5F104ADDSP [DX1026]
R5F104AEDSP [DX1026]
R5F104AFDSP [DX1026]
R5F104AGDSP [DX1026]
R5F104AHDSP [DX1026]
R5F104AJDSP [DX1026]
R5F104AKDSP [DX1026]
R5F104ALDSP [DX1026]
R5F104BAANA [DX4015]
R5F104BADNA [DX4015]
R5F104BCANA [DX4015]
R5F104BCDNA [DX4015]
R5F104BDANA [DX4015]
R5F104BDDNA [DX4015]
R5F104BEANA [DX4015]
R5F104BEDNA [DX4015]
R5F104BFANA [DX4015]
R5F104BFDNA [DX4015]
R5F104BGANA [DX4015]
R5F104BGDNA [DX4015]
R5F104BHANA [DX4015]
R5F104BHDNA [DX4015]
R5F104BJANA [DX4015]
R5F104BJDNA [DX4015]
R5F104BKANA [DX4015]
R5F104BKDNA [DX4015]
R5F104BLANA [DX4015]
R5F102A8ASP [DX1027]
R5F102A9ASP [DX1027]
R5F102AAASP [DX1027]
R5F10366ASP [DX1067]
R5F10367ASP [DX1067]
R5F10368ASP [DX1067]
R5F10369ASP [DX1067]
R5F1036AASP [DX1067]
R5F10376ANA [DX4012]
R5F10377ANA [DX4012]
R5F10378ANA [DX4012]
R5F10379ANA [DX4012]
R5F1037AANA [DX4012]
R5F103A6ASP [DX1027]
R5F103A7ASP [DX1027]
R5F103A8ASP [DX1027]
R5F103A9ASP [DX1027]
R5F103AAASP [DX1027]
R5F104AAASP [DX1026]
R5F104ACASP [DX1026]
R5F104ADASP [DX1026]
R5F104AEASP [DX1026]
R5F104AFASP [DX1026]
R5F104AGASP [DX1026]
R5F104AHASP [DX1026]
R5F104AJASP [DX1026]
R5F104AKASP [DX1026]
R5F104ALASP [DX1026]
R5F104BAAFP [DX3001]
R5F104BADFP [DX3001]
R5F104BCAFP [DX3001]
R5F104BCDFP [DX3001]
R5F104BDAFP [DX3001]
R5F104BDDFP [DX3001]
R5F104BEAFP [DX3001]
R5F104BEDFP [DX3001]
R5F104BFAFP [DX3001]
R5F104BFDFP [DX3001]
R5F104BGAFP [DX3001]
R5F104BGDFP [DX3001]
R5F104BHAFP [DX3001]
R5F104BHDFP [DX3001]
R5F104BJAFP [DX3001]
R5F104BJDFP [DX3001]
R5F104BKAFP [DX3001]
R5F104BKDFP [DX3001]
R5F104BLAFP [DX3001]
R5F104BLDFP [DX3001]

R5F104BLDNA [DX4015]
R5F104CADLA [DX0001]
R5F104CCDLA [DX0001]
R5F104CDDLA [DX0001]
R5F104CEDLA [DX0001]
R5F104CFDLA [DX0001]
R5F104CGDLA [DX0001]
R5F104CHDLA [DX0001]
R5F104CJDLA [DX0001]
R5F104CKDLA [DX0001]
R5F104CLDLA [DX0001]
R5F104EADNA [DX4017]
R5F104ECDNA [DX4017]
R5F104EDDNA [DX4017]
R5F104EEDNA [DX4017]
R5F104EFDNA [DX4017]
R5F104EGDNA [DX4017]
R5F104EHDNA [DX4017]
R5F104EJDNA [DX4017]
R5F104EKDNA [DX4017]
R5F104ELDNA [DX4017]
R5F104FADFP [DX3002]
R5F104FCDFP [DX3002]
R5F104FDDFP [DX3002]
R5F104FEDFP [DX3002]
R5F104FFDFP [DX3002]
R5F104FGDFP [DX3002]
R5F104FHDFP [DX3002]
R5F104FJDFP [DX3002]
R5F104FKDFP [DX3002]
R5F104FLDFP [DX3002]
R5F104GAANA [DX4021]
R5F104GADNA [DX4021]
R5F104GCANA [DX4021]
R5F104GCDNA [DX4021]
R5F104GDANA [DX4021]
R5F104GDDNA [DX4021]
R5F104GEANA [DX4021]
R5F104GEDNA [DX4021]
R5F104GFANA [DX4021]
R5F104GFDNA [DX4021]
R5F104GGANA [DX4021]
R5F104GGDNA [DX4021]
R5F104GHANA [DX4021]
R5F104GHDNA [DX4021]
R5F104GJANA [DX4021]
R5F104GJDNA [DX4021]
R5F104GKANA [DX4021]
R5F104CAALA [DX0001]
R5F104CCALA [DX0001]
R5F104CDALA [DX0001]
R5F104CEALA [DX0001]
R5F104CFALA [DX0001]
R5F104CGALA [DX0001]
R5F104CHALA [DX0001]
R5F104CJALA [DX0001]
R5F104CKALA [DX0001]
R5F104CLALA [DX0001]
R5F104EAANA [DX4017]
R5F104ECANA [DX4017]
R5F104EDANA [DX4017]
R5F104EEANA [DX4017]
R5F104EFANA [DX4017]
R5F104EGANA [DX4017]
R5F104EHANA [DX4017]
R5F104EJANA [DX4017]
R5F104EKANA [DX4017]
R5F104ELANA [DX4017]
R5F104FAAFP [DX3002]
R5F104FCAFP [DX3002]
R5F104FDAFP [DX3002]
R5F104FEAFP [DX3002]
R5F104FFAFP [DX3002]
R5F104FGAFP [DX3002]
R5F104FHAFP [DX3002]
R5F104FJAFP [DX3002]
R5F104FKAFP [DX3002]
R5F104FLAFP [DX3002]
R5F104GAAFB [DX3007]
R5F104GADFB [DX3007]
R5F104GCAFB [DX3007]
R5F104GCDFB [DX3007]
R5F104GDAFB [DX3007]
R5F104GDDFB [DX3007]
R5F104GEAFB [DX3007]
R5F104GEDFB [DX3007]
R5F104GFAFB [DX3007]
R5F104GFDFB [DX3007]
R5F104GGAFB [DX3007]
R5F104GGDFB [DX3007]
R5F104GHAFB [DX3007]
R5F104GHDFB [DX3007]
R5F104GJAFB [DX3007]
R5F104GJDFB [DX3007]
R5F104GKAFB [DX3007]
R5F104GKDFB [DX3007]

R5F104GKDNA [DX4021]
R5F104GLANA [DX4021]
R5F104GLDNA [DX4021]
R5F104JCDFA [DX3010]
R5F104JDDFA [DX3010]
R5F104JEDFA [DX3010]
R5F104JFDFA [DX3010]
R5F104JGDFA [DX3010]
R5F104JHDFA [DX3010]
R5F104JJDFA [DX3010]
R5F104JKDFA [DX3010]
R5F104JLDFA [DX3010]
R5F104LCAFB [DX3011]
R5F104LCALA [DX0001]
R5F104LCDFB [DX3011]
R5F104LCDLA [DX0001]
R5F104LDAFB [DX3011]
R5F104LDALA [DX0001]
R5F104LDDFB [DX3011]
R5F104LDDLA [DX0001]
R5F104LEAFB [DX3011]
R5F104LEALA [DX0001]
R5F104LEDFB [DX3011]
R5F104LEDLA [DX0001]
R5F104LFAFB [DX3011]
R5F104LFALA [DX0001]
R5F104LFDFB [DX3011]
R5F104LFDLA [DX0001]
R5F104LGAFB [DX3011]
R5F104LGALA [DX0001]
R5F104LGDFB [DX3011]
R5F104LGDLA [DX0001]
R5F104LHAFB [DX3011]
R5F104LHALA [DX0001]
R5F104LHDFB [DX3011]
R5F104LHDLA [DX0001]
R5F104LJAFB [DX3011]
R5F104LJALA [DX0001]
R5F104LJDFB [DX3011]
R5F104LJDLA [DX0001]
R5F104LKAFB [DX3011]
R5F104LKALA [DX0001]
R5F104LKDFB [DX3011]
R5F104LKDLA [DX0001]
R5F104LLAFB [DX3011]
R5F104LLALA [DX0001]
R5F104LLDFB [DX3011]
R5F104LLDLA [DX0001]
R5F104GLAFB [DX3007]
R5F104GLDFB [DX3007]
R5F104JCAFA [DX3010]
R5F104JDAFA [DX3010]
R5F104JEAFA [DX3010]
R5F104JFAFA [DX3010]
R5F104JGAFA [DX3010]
R5F104JHAFA [DX3010]
R5F104JJAFA [DX3010]
R5F104JKAFA [DX3010]
R5F104JLAFA [DX3010]
R5F104LCAFA [DX3012]
R5F104LCAFP [DX3013]
R5F104LCDFA [DX3012]
R5F104LCDFP [DX3013]
R5F104LDAFA [DX3012]
R5F104LDAFP [DX3013]
R5F104LDDFA [DX3012]
R5F104LDDFP [DX3013]
R5F104LEAFA [DX3012]
R5F104LEAFP [DX3013]
R5F104LEDFA [DX3012]
R5F104LEDFP [DX3013]
R5F104LFAFA [DX3012]
R5F104LFAFP [DX3013]
R5F104LFDFA [DX3012]
R5F104LFDFP [DX3013]
R5F104LGAFA [DX3012]
R5F104LGAFP [DX3013]
R5F104LGDFA [DX3012]
R5F104LGDFP [DX3013]
R5F104LHAFA [DX3012]
R5F104LHAFP [DX3013]
R5F104LHDFA [DX3012]
R5F104LHDFP [DX3013]
R5F104LJAFA [DX3012]
R5F104LJAFP [DX3013]
R5F104LJDFA [DX3012]
R5F104LJDFP [DX3013]
R5F104LKAFA [DX3012]
R5F104LKAFP [DX3013]
R5F104LKDFA [DX3012]
R5F104LKDFP [DX3013]
R5F104LLAFA [DX3012]
R5F104LLAFP [DX3013]
R5F104LLDFA [DX3012]
R5F104LLDFP [DX3013]
R5F104MCAFA [DX3017]

R5F104MCAFB [DX3016]
R5F104MCDFB [DX3016]
R5F104MDAFB [DX3016]
R5F104MDDFB [DX3016]
R5F104MEAFB [DX3016]
R5F104MEDFB [DX3016]
R5F104MFAFB [DX3016]
R5F104MFDFB [DX3016]
R5F104MGAFB [DX3016]
R5F104MGDFB [DX3016]
R5F104MHAFB [DX3016]
R5F104MHDFB [DX3016]
R5F104MJAFB [DX3016]
R5F104MJDFB [DX3016]
R5F104MKAFB [DX3016]
R5F104MKDFB [DX3016]
R5F104MLAFB [DX3016]
R5F104MLDFB [DX3016]
R5F104PCAFB [DX3021]
R5F104PCDFB [DX3021]
R5F104PDAFB [DX3021]
R5F104PDDFB [DX3021]
R5F104PEAFB [DX3021]
R5F104PEDFB [DX3021]
R5F104PFAFB [DX3021]
R5F104PFDFB [DX3021]
R5F104PGAFB [DX3021]
R5F104PGDFB [DX3021]
R5F104PHAFB [DX3021]
R5F104PHDFB [DX3021]
R5F104PJAFB [DX3021]
R5F104PJDFB [DX3021]
R5F104PKAFB [DX3021]
R5F104PKDFB [DX3021]
R5F104PLAFB [DX3021]
R5F104PLDFB [DX3021]
R5F104SCDFB [DX3031]
R5F104SDDFB [DX3031]
R5F104SEDFB [DX3031]
R5F104SFDFB [DX3031]
R5F104SGDFB [DX3031]
R5F104SHDFB [DX3031]
R5F104SJDFB [DX3031]
R5F104SKDFB [DX3031]
R5F104SLDFB [DX3031]
R5F1076EGSP [DX1001]
R5F107AEGSP [DX1087]
R5F107DEGSP [DX1027]
R5F104MCDFA [DX3017]
R5F104MDAFA [DX3017]
R5F104MDDFA [DX3017]
R5F104MEAFA [DX3017]
R5F104MEDFA [DX3017]
R5F104MFAFA [DX3017]
R5F104MFDFA [DX3017]
R5F104MGAFA [DX3017]
R5F104MGDFA [DX3017]
R5F104MHAFA [DX3017]
R5F104MHDFA [DX3017]
R5F104MJAFA [DX3017]
R5F104MJDFA [DX3017]
R5F104MKAFA [DX3017]
R5F104MKDFA [DX3017]
R5F104MLAFA [DX3017]
R5F104MLDFA [DX3017]
R5F104PCAFA [DX3023]
R5F104PCDFA [DX3023]
R5F104PDAFA [DX3023]
R5F104PDDFA [DX3023]
R5F104PEAFA [DX3023]
R5F104PEDFA [DX3023]
R5F104PFAFA [DX3023]
R5F104PFDFA [DX3023]
R5F104PGAFA [DX3023]
R5F104PGDFA [DX3023]
R5F104PHAFA [DX3023]
R5F104PHDFA [DX3023]
R5F104PJAFA [DX3023]
R5F104PJDFA [DX3023]
R5F104PKAFA [DX3023]
R5F104PKDFA [DX3023]
R5F104PLAFA [DX3023]
R5F104PLDFA [DX3023]
R5F104SCAFB [DX3031]
R5F104SDAFB [DX3031]
R5F104SEAFB [DX3031]
R5F104SFAFB [DX3031]
R5F104SGAFB [DX3031]
R5F104SHAFB [DX3031]
R5F104SJAFB [DX3031]
R5F104SKAFB [DX3031]
R5F104SLAFB [DX3031]
R5F1076CGSP [DX1001]
R5F107ACGSP [DX1087]
R5F107DCGSP [DX1027]
R5F10968JSP [DX1026]

R5F1096AJSP [DX1026]
R5F1096BJSP [DX1026]
R5F1096CJSP [DX1026]
R5F1096DJSP [DX1026]
R5F1096EJSP [DX1026]
R5F1096FJSP [DX1026]
R5F1096GJSP [DX1026]
R5F1096HJSP [DX1026]
R5F1096JJSP [DX1026]
R5F1096KJSP [DX1026]
R5F1096LJSP [DX1026]
R5F109A8JSP [DX1087]
R5F109AAJSP [DX1087]
R5F109ABJSP [DX1087]
R5F109ACJSP [DX1087]
R5F109ADJSP [DX1087]
R5F109AEJSP [DX1087]
R5F109AFJSP [DX1087]
R5F109AGJSP [DX1087]
R5F109AHJSP [DX1087]
R5F109AJJSP [DX1087]
R5F109AKJSP [DX1087]
R5F109ALJSP [DX1087]
R5F109B8JFP [DX3001]
R5F109B8JNA [DX4015]
R5F109BAJFP [DX3001]
R5F109BAJNA [DX4015]
R5F109BBJFP [DX3001]
R5F109BBJNA [DX4015]
R5F109BCJFP [DX3001]
R5F109BCJNA [DX4015]
R5F109BDJFP [DX3001]
R5F109BDJNA [DX4015]
R5F109BEJFP [DX3001]
R5F109BEJNA [DX4015]
R5F109BFJFP [DX3001]
R5F109BFJNA [DX4015]
R5F109BGJFP [DX3001]
R5F109BGJNA [DX4015]
R5F109BHJFP [DX3001]
R5F109BHJNA [DX4015]
R5F109BJJFP [DX3001]
R5F109BJJNA [DX4015]
R5F109BKJFP [DX3001]
R5F109BKJNA [DX4015]
R5F109BLJFP [DX3001]
R5F109BLJNA [DX4015]
R5F109C8JLA [DX0001]
R5F109CAJLA [DX0001]
R5F109CBJLA [DX0001]
R5F109CCJLA [DX0001]
R5F109CDJLA [DX0001]
R5F109CEJLA [DX0001]
R5F109CFJLA [DX0001]
R5F109CGJLA [DX0001]
R5F109CHJLA [DX0001]
R5F109CJJLA [DX0001]
R5F109CKJLA [DX0001]
R5F109CLJLA [DX0001]
R5F109E8JNA [DX4017]
R5F109EAJNA [DX4017]
R5F109EBJNA [DX4017]
R5F109ECJNA [DX4017]
R5F109EDJNA [DX4017]
R5F109EEJNA [DX4017]
R5F109EFJNA [DX4017]
R5F109EGJNA [DX4017]
R5F109EHJNA [DX4017]
R5F109EJJNA [DX4017]
R5F109EKJNA [DX4017]
R5F109ELJNA [DX4017]
R5F109F8JFP [DX3002]
R5F109FAJFP [DX3002]
R5F109FBJFP [DX3002]
R5F109FCJFP [DX3002]
R5F109FDJFP [DX3002]
R5F109FEJFP [DX3002]
R5F109FFJFP [DX3002]
R5F109FGJFP [DX3002]
R5F109FHJFP [DX3002]
R5F109FJJFP [DX3002]
R5F109FKJFP [DX3002]
R5F109FLJFP [DX3002]
R5F109G8JFB [DX3007]
R5F109G8JNA [DX4021]
R5F109GAJFB [DX3007]
R5F109GAJNA [DX4021]
R5F109GBJFB [DX3007]
R5F109GBJNA [DX4021]
R5F109GCJFB [DX3007]
R5F109GCJNA [DX4021]
R5F109GDJFB [DX3007]
R5F109GDJNA [DX4021]
R5F109GEJFB [DX3007]
R5F109GEJNA [DX4021]
R5F109GFJFB [DX3007]

R5F109GFJNA [DX4021]
R5F109GGJNA [DX4021]
R5F109GHJNA [DX4021]
R5F109GJJNA [DX4021]
R5F109GKJNA [DX4021]
R5F109GLJNA [DX4021]
R5F109LAJFB [DX3011]
R5F109LCJFB [DX3011]
R5F109LEJFB [DX3011]
R5F109LGJFB [DX3011]
R5F109LJJFB [DX3011]
R5F109LLJFB [DX3011]
R5F10A68LSP [DX1026]
R5F10A6AKSP [DX1026]
R5F10A6AYSP [DX1026]
R5F10A6BLSP [DX1026]
R5F10A6CKSP [DX1026]
R5F10A6CYSP [DX1026]
R5F10A6DLSP [DX1026]
R5F10A6EKSP [DX1026]
R5F10A6EYSP [DX1026]
R5F10A6FLSP [DX1026]
R5F10A6GKSP [DX1026]
R5F10A6GYSP [DX1026]
R5F10A6HLSP [DX1026]
R5F10A6KKSP [DX1026]
R5F10A6KYSP [DX1026]
R5F10A6LLSP [DX1026]
R5F10A6YYSP [DX1026]
R5F10AA8LSP [DX1087]
R5F10AAAKSP [DX1087]
R5F10AAAYSP [DX1087]
R5F10AABLSP [DX1087]
R5F10AACKSP [DX1087]
R5F10AACYSP [DX1087]
R5F10AADLSP [DX1087]
R5F10AAEKSP [DX1087]
R5F10AAEYSP [DX1087]
R5F10AAFLSP [DX1087]
R5F10AAGKSP [DX1087]
R5F10AAGYSP [DX1087]
R5F10AAHLSP [DX1087]
R5F10AAKKSP [DX1087]
R5F10AAKYSP [DX1087]
R5F10AALLSP [DX1087]
R5F10AAYYSP [DX1087]
R5F10AB8KNA [DX4015]
R5F10AB8LNA [DX4015]
R5F109GGJFB [DX3007]
R5F109GHJFB [DX3007]
R5F109GJJFB [DX3007]
R5F109GKJFB [DX3007]
R5F109GLJFB [DX3007]
R5F109L8JFB [DX3011]
R5F109LBJFB [DX3011]
R5F109LDJFB [DX3011]
R5F109LFJFB [DX3011]
R5F109LHJFB [DX3011]
R5F109LKJFB [DX3011]
R5F10A68KSP [DX1026]
R5F10A68YSP [DX1026]
R5F10A6ALSP [DX1026]
R5F10A6BKSP [DX1026]
R5F10A6BYSP [DX1026]
R5F10A6CLSP [DX1026]
R5F10A6DKSP [DX1026]
R5F10A6DYSP [DX1026]
R5F10A6ELSP [DX1026]
R5F10A6FKSP [DX1026]
R5F10A6FYSP [DX1026]
R5F10A6GLSP [DX1026]
R5F10A6HKSP [DX1026]
R5F10A6HYSP [DX1026]
R5F10A6KLSP [DX1026]
R5F10A6LKSP [DX1026]
R5F10A6LYSP [DX1026]
R5F10AA8KSP [DX1087]
R5F10AA8YSP [DX1087]
R5F10AAALSP [DX1087]
R5F10AABKSP [DX1087]
R5F10AABYSP [DX1087]
R5F10AACLSP [DX1087]
R5F10AADKSP [DX1087]
R5F10AADYSP [DX1087]
R5F10AAELSP [DX1087]
R5F10AAFKSP [DX1087]
R5F10AAFYSP [DX1087]
R5F10AAGLSP [DX1087]
R5F10AAHKSP [DX1087]
R5F10AAHYSP [DX1087]
R5F10AAKLSP [DX1087]
R5F10AALKSP [DX1087]
R5F10AALYSP [DX1087]
R5F10AB8KFP [DX3001]
R5F10AB8LFP [DX3001]
R5F10AB8YFP [DX3001]

R5F10AB8YNA [DX4015]
R5F10ABAKNA [DX4015]
R5F10ABALNA [DX4015]
R5F10ABAYNA [DX4015]
R5F10ABBKNA [DX4015]
R5F10ABBLNA [DX4015]
R5F10ABBYNA [DX4015]
R5F10ABCKNA [DX4015]
R5F10ABCLNA [DX4015]
R5F10ABCYNA [DX4015]
R5F10ABDKNA [DX4015]
R5F10ABDLNA [DX4015]
R5F10ABDYNA [DX4015]
R5F10ABEKNA [DX4015]
R5F10ABELNA [DX4015]
R5F10ABEYNA [DX4015]
R5F10ABFKNA [DX4015]
R5F10ABFLNA [DX4015]
R5F10ABFYNA [DX4015]
R5F10ABGKNA [DX4015]
R5F10ABGLNA [DX4015]
R5F10ABGYNA [DX4015]
R5F10ABHKNA [DX4015]
R5F10ABHLNA [DX4015]
R5F10ABHYNA [DX4015]
R5F10ABKKNA [DX4015]
R5F10ABKLNA [DX4015]
R5F10ABKYNA [DX4015]
R5F10ABLKNA [DX4015]
R5F10ABLLNA [DX4015]
R5F10ABLYNA [DX4015]
R5F10ABYYNA [DX4015]
R5F10AC8LLA [DX0001]
R5F10ACAKLA [DX0001]
R5F10ACAYLA [DX0001]
R5F10ACBLLA [DX0001]
R5F10ACCKLA [DX0001]
R5F10ACCYLA [DX0001]
R5F10ACDLLA [DX0001]
R5F10ACEKLA [DX0001]
R5F10ACEYLA [DX0001]
R5F10ACFLLA [DX0001]
R5F10ACGKLA [DX0001]
R5F10ACGYLA [DX0001]
R5F10ACHLLA [DX0001]
R5F10ACKKLA [DX0001]
R5F10ACKYLA [DX0001]
R5F10ACLLLA [DX0001]
R5F10ABAKFP [DX3001]
R5F10ABALFP [DX3001]
R5F10ABAYFP [DX3001]
R5F10ABBKFP [DX3001]
R5F10ABBLFP [DX3001]
R5F10ABBYFP [DX3001]
R5F10ABCKFP [DX3001]
R5F10ABCLFP [DX3001]
R5F10ABCYFP [DX3001]
R5F10ABDKFP [DX3001]
R5F10ABDLFP [DX3001]
R5F10ABDYFP [DX3001]
R5F10ABEKFP [DX3001]
R5F10ABELFP [DX3001]
R5F10ABEYFP [DX3001]
R5F10ABFKFP [DX3001]
R5F10ABFLFP [DX3001]
R5F10ABFYFP [DX3001]
R5F10ABGKFP [DX3001]
R5F10ABGLFP [DX3001]
R5F10ABGYFP [DX3001]
R5F10ABHKFP [DX3001]
R5F10ABHLFP [DX3001]
R5F10ABHYFP [DX3001]
R5F10ABKKFP [DX3001]
R5F10ABKLFP [DX3001]
R5F10ABKYFP [DX3001]
R5F10ABLKFP [DX3001]
R5F10ABLLFP [DX3001]
R5F10ABLYFP [DX3001]
R5F10ABYYFP [DX3001]
R5F10AC8KLA [DX0001]
R5F10AC8YLA [DX0001]
R5F10ACALLA [DX0001]
R5F10ACBKLA [DX0001]
R5F10ACBYLA [DX0001]
R5F10ACCLLA [DX0001]
R5F10ACDKLA [DX0001]
R5F10ACDYLA [DX0001]
R5F10ACELLA [DX0001]
R5F10ACFKLA [DX0001]
R5F10ACFYLA [DX0001]
R5F10ACGLLA [DX0001]
R5F10ACHKLA [DX0001]
R5F10ACHYLA [DX0001]
R5F10ACKLLA [DX0001]
R5F10ACLKLA [DX0001]
R5F10ACLYLA [DX0001]

R5F10ACYYLA [DX0001]
R5F10AE8KNA [DX4017]
R5F10AE8LNA [DX4017]
R5F10AE8YNA [DX4017]
R5F10AEAKNA [DX4017]
R5F10AEALNA [DX4017]
R5F10AEAYNA [DX4017]
R5F10AEBKNA [DX4017]
R5F10AEBLNA [DX4017]
R5F10AEBYNA [DX4017]
R5F10AECKNA [DX4017]
R5F10AECLNA [DX4017]
R5F10AECYNA [DX4017]
R5F10AEDKNA [DX4017]
R5F10AEDLNA [DX4017]
R5F10AEDYNA [DX4017]
R5F10AEEKNA [DX4017]
R5F10AEELNA [DX4017]
R5F10AEEYNA [DX4017]
R5F10AEFKNA [DX4017]
R5F10AEFLNA [DX4017]
R5F10AEFYNA [DX4017]
R5F10AEGKNA [DX4017]
R5F10AEGLNA [DX4017]
R5F10AEGYNA [DX4017]
R5F10AEHKNA [DX4017]
R5F10AEHLNA [DX4017]
R5F10AEHYNA [DX4017]
R5F10AEKKNA [DX4017]
R5F10AEKLNA [DX4017]
R5F10AEKYNA [DX4017]
R5F10AELKNA [DX4017]
R5F10AELLNA [DX4017]
R5F10AELYNA [DX4017]
R5F10AEYYNA [DX4017]
R5F10AF8KFP [DX3002]
R5F10AF8LFP [DX3002]
R5F10AF8YFP [DX3002]
R5F10AFAKFP [DX3002]
R5F10AFALFP [DX3002]
R5F10AFAYFP [DX3002]
R5F10AFBKFP [DX3002]
R5F10AFBLFP [DX3002]
R5F10AFBYFP [DX3002]
R5F10AFCKFP [DX3002]
R5F10AFCLFP [DX3002]
R5F10AFCYFP [DX3002]
R5F10AFDKFP [DX3002]
R5F10AFDLFP [DX3002]
R5F10AFDYFP [DX3002]
R5F10AFEKFP [DX3002]
R5F10AFELFP [DX3002]
R5F10AFEYFP [DX3002]
R5F10AFFKFP [DX3002]
R5F10AFFLFP [DX3002]
R5F10AFFYFP [DX3002]
R5F10AFGKFP [DX3002]
R5F10AFGLFP [DX3002]
R5F10AFGYFP [DX3002]
R5F10AFHKFP [DX3002]
R5F10AFHLFP [DX3002]
R5F10AFHYFP [DX3002]
R5F10AFKKFP [DX3002]
R5F10AFKLFP [DX3002]
R5F10AFKYFP [DX3002]
R5F10AFLKFP [DX3002]
R5F10AFLLFP [DX3002]
R5F10AFLYFP [DX3002]
R5F10AFYYFP [DX3002]
R5F10AG8KFB [DX3007]
R5F10AG8KNA [DX4021]
R5F10AG8LFB [DX3007]
R5F10AG8LNA [DX4021]
R5F10AG8YFB [DX3007]
R5F10AG8YNA [DX4021]
R5F10AGAKFB [DX3007]
R5F10AGAKNA [DX4021]
R5F10AGALFB [DX3007]
R5F10AGALNA [DX4021]
R5F10AGAYFB [DX3007]
R5F10AGAYNA [DX4021]
R5F10AGBKFB [DX3007]
R5F10AGBKNA [DX4021]
R5F10AGBLFB [DX3007]
R5F10AGBLNA [DX4021]
R5F10AGBYFB [DX3007]
R5F10AGBYNA [DX4021]
R5F10AGCKFB [DX3007]
R5F10AGCKNA [DX4021]
R5F10AGCLFB [DX3007]
R5F10AGCLNA [DX4021]
R5F10AGCYFB [DX3007]
R5F10AGCYNA [DX4021]
R5F10AGDKFB [DX3007]
R5F10AGDKNA [DX4021]
R5F10AGDLFB [DX3007]

R5F10AGDLNA [DX4021]
R5F10AGDYNA [DX4021]
R5F10AGEKNA [DX4021]
R5F10AGELNA [DX4021]
R5F10AGEYNA [DX4021]
R5F10AGFKNA [DX4021]
R5F10AGFLNA [DX4021]
R5F10AGFYNA [DX4021]
R5F10AGGKNA [DX4021]
R5F10AGGLNA [DX4021]
R5F10AGGYNA [DX4021]
R5F10AGHKNA [DX4021]
R5F10AGHLNA [DX4021]
R5F10AGHYNA [DX4021]
R5F10AGKKNA [DX4021]
R5F10AGKLNA [DX4021]
R5F10AGKYNA [DX4021]
R5F10AGLKNA [DX4021]
R5F10AGLLNA [DX4021]
R5F10AGLYNA [DX4021]
R5F10AGYYNA [DX4021]
R5F10AL8LFB [DX3011]
R5F10ALAKFB [DX3011]
R5F10ALAYFB [DX3011]
R5F10ALBLFB [DX3011]
R5F10ALCKFB [DX3011]
R5F10ALCYFB [DX3011]
R5F10ALDLFB [DX3011]
R5F10ALEKFB [DX3011]
R5F10ALEYFB [DX3011]
R5F10ALFLFB [DX3011]
R5F10ALGKFB [DX3011]
R5F10ALGYFB [DX3011]
R5F10ALHLFB [DX3011]
R5F10ALKKFB [DX3011]
R5F10ALKYFB [DX3011]
R5F10ALLLFB [DX3011]
R5F10ALYYFB [DX3011]
R5F10B68LSP [DX1026]
R5F10B6AKSP [DX1026]
R5F10B6AYSP [DX1026]
R5F10B6BLSP [DX1026]
R5F10B6CKSP [DX1026]
R5F10B6CYSP [DX1026]
R5F10B6DLSP [DX1026]
R5F10B6EKSP [DX1026]
R5F10B6EYSP [DX1026]
R5F10B6FLSP [DX1026]
R5F10AGDYFB [DX3007]
R5F10AGEKFB [DX3007]
R5F10AGELFB [DX3007]
R5F10AGEYFB [DX3007]
R5F10AGFKFB [DX3007]
R5F10AGFLFB [DX3007]
R5F10AGFYFB [DX3007]
R5F10AGGKFB [DX3007]
R5F10AGGLFB [DX3007]
R5F10AGGYFB [DX3007]
R5F10AGHKFB [DX3007]
R5F10AGHLFB [DX3007]
R5F10AGHYFB [DX3007]
R5F10AGKKFB [DX3007]
R5F10AGKLFB [DX3007]
R5F10AGKYFB [DX3007]
R5F10AGLKFB [DX3007]
R5F10AGLLFB [DX3007]
R5F10AGLYFB [DX3007]
R5F10AGYYFB [DX3007]
R5F10AL8KFB [DX3011]
R5F10AL8YFB [DX3011]
R5F10ALALFB [DX3011]
R5F10ALBKFB [DX3011]
R5F10ALBYFB [DX3011]
R5F10ALCLFB [DX3011]
R5F10ALDKFB [DX3011]
R5F10ALDYFB [DX3011]
R5F10ALELFB [DX3011]
R5F10ALFKFB [DX3011]
R5F10ALFYFB [DX3011]
R5F10ALGLFB [DX3011]
R5F10ALHKFB [DX3011]
R5F10ALHYFB [DX3011]
R5F10ALKLFB [DX3011]
R5F10ALLKFB [DX3011]
R5F10ALLYFB [DX3011]
R5F10B68KSP [DX1026]
R5F10B68YSP [DX1026]
R5F10B6ALSP [DX1026]
R5F10B6BKSP [DX1026]
R5F10B6BYSP [DX1026]
R5F10B6CLSP [DX1026]
R5F10B6DKSP [DX1026]
R5F10B6DYSP [DX1026]
R5F10B6ELSP [DX1026]
R5F10B6FKSP [DX1026]
R5F10B6FYSP [DX1026]

R5F10B6GKSP [DX1026]
R5F10B6GLSP [DX1026]
R5F10B6GYSP [DX1026]
R5F10B6HKSP [DX1026]
R5F10B6HLSP [DX1026]
R5F10B6HYSP [DX1026]
R5F10B6KKSP [DX1026]
R5F10B6KLSP [DX1026]
R5F10B6KYSP [DX1026]
R5F10B6LKSP [DX1026]
R5F10B6LLSP [DX1026]
R5F10B6LYSP [DX1026]
R5F10B6YYSP [DX1026]
R5F10BA8KSP [DX1087]
R5F10BA8LSP [DX1087]
R5F10BA8YSP [DX1087]
R5F10BAAKSP [DX1087]
R5F10BAALSP [DX1087]
R5F10BAAYSP [DX1087]
R5F10BABKSP [DX1087]
R5F10BABLSP [DX1087]
R5F10BABYSP [DX1087]
R5F10BACKSP [DX1087]
R5F10BACLSP [DX1087]
R5F10BACYSP [DX1087]
R5F10BADKSP [DX1087]
R5F10BADLSP [DX1087]
R5F10BADYSP [DX1087]
R5F10BAEKSP [DX1087]
R5F10BAELSP [DX1087]
R5F10BAEYSP [DX1087]
R5F10BAFKSP [DX1087]
R5F10BAFLSP [DX1087]
R5F10BAFYSP [DX1087]
R5F10BAGKSP [DX1087]
R5F10BAGLSP [DX1087]
R5F10BAGYSP [DX1087]
R5F10BAHKSP [DX1087]
R5F10BAHLSP [DX1087]
R5F10BAHYSP [DX1087]
R5F10BAKKSP [DX1087]
R5F10BAKLSP [DX1087]
R5F10BAKYSP [DX1087]
R5F10BALKSP [DX1087]
R5F10BALLSP [DX1087]
R5F10BALYSP [DX1087]
R5F10BAYYSP [DX1087]
R5F10BB8KFP [DX3001]
R5F10BB8KNA [DX4015]
R5F10BB8LFP [DX3001]
R5F10BB8LNA [DX4015]
R5F10BB8YFP [DX3001]
R5F10BB8YNA [DX4015]
R5F10BBAKFP [DX3001]
R5F10BBAKNA [DX4015]
R5F10BBALFP [DX3001]
R5F10BBALNA [DX4015]
R5F10BBAYFP [DX3001]
R5F10BBAYNA [DX4015]
R5F10BBBKFP [DX3001]
R5F10BBBKNA [DX4015]
R5F10BBBLFP [DX3001]
R5F10BBBLNA [DX4015]
R5F10BBBYFP [DX3001]
R5F10BBBYNA [DX4015]
R5F10BBCKFP [DX3001]
R5F10BBCKNA [DX4015]
R5F10BBCLFP [DX3001]
R5F10BBCLNA [DX4015]
R5F10BBCYFP [DX3001]
R5F10BBCYNA [DX4015]
R5F10BBDKFP [DX3001]
R5F10BBDKNA [DX4015]
R5F10BBDLFP [DX3001]
R5F10BBDLNA [DX4015]
R5F10BBDYFP [DX3001]
R5F10BBDYNA [DX4015]
R5F10BBEKFP [DX3001]
R5F10BBEKNA [DX4015]
R5F10BBELFP [DX3001]
R5F10BBELNA [DX4015]
R5F10BBEYFP [DX3001]
R5F10BBEYNA [DX4015]
R5F10BBFKFP [DX3001]
R5F10BBFKNA [DX4015]
R5F10BBFLFP [DX3001]
R5F10BBFLNA [DX4015]
R5F10BBFYFP [DX3001]
R5F10BBFYNA [DX4015]
R5F10BBGKFP [DX3001]
R5F10BBGKNA [DX4015]
R5F10BBGLFP [DX3001]
R5F10BBGLNA [DX4015]
R5F10BBGYFP [DX3001]
R5F10BBGYNA [DX4015]
R5F10BBHKFP [DX3001]

R5F10BBHKNA [DX4015]
R5F10BBHLNA [DX4015]
R5F10BBHYNA [DX4015]
R5F10BBKKNA [DX4015]
R5F10BBKLNA [DX4015]
R5F10BBKYNA [DX4015]
R5F10BBLKNA [DX4015]
R5F10BBLLNA [DX4015]
R5F10BBLYNA [DX4015]
R5F10BBYYNA [DX4015]
R5F10BC8LLA [DX0001]
R5F10BCAKLA [DX0001]
R5F10BCAYLA [DX0001]
R5F10BCBLLA [DX0001]
R5F10BCCKLA [DX0001]
R5F10BCCYLA [DX0001]
R5F10BCDLLA [DX0001]
R5F10BCEKLA [DX0001]
R5F10BCEYLA [DX0001]
R5F10BCFLLA [DX0001]
R5F10BCGKLA [DX0001]
R5F10BCGYLA [DX0001]
R5F10BCHLLA [DX0001]
R5F10BCKKLA [DX0001]
R5F10BCKYLA [DX0001]
R5F10BCLLLA [DX0001]
R5F10BCYYLA [DX0001]
R5F10BE8LNA [DX4017]
R5F10BEAKNA [DX4017]
R5F10BEAYNA [DX4017]
R5F10BEBLNA [DX4017]
R5F10BECKNA [DX4017]
R5F10BECYNA [DX4017]
R5F10BEDLNA [DX4017]
R5F10BEEKNA [DX4017]
R5F10BEEYNA [DX4017]
R5F10BEFLNA [DX4017]
R5F10BEGKNA [DX4017]
R5F10BEGYNA [DX4017]
R5F10BEHLNA [DX4017]
R5F10BEKKNA [DX4017]
R5F10BEKYNA [DX4017]
R5F10BELLNA [DX4017]
R5F10BEYYNA [DX4017]
R5F10BF8LFP [DX3002]
R5F10BFAKFP [DX3002]
R5F10BFAYFP [DX3002]
R5F10BFBLFP [DX3002]
R5F10BBHLFP [DX3001]
R5F10BBHYFP [DX3001]
R5F10BBKKFP [DX3001]
R5F10BBKLFP [DX3001]
R5F10BBKYFP [DX3001]
R5F10BBLKFP [DX3001]
R5F10BBLLFP [DX3001]
R5F10BBLYFP [DX3001]
R5F10BBYYFP [DX3001]
R5F10BC8KLA [DX0001]
R5F10BC8YLA [DX0001]
R5F10BCALLA [DX0001]
R5F10BCBKLA [DX0001]
R5F10BCBYLA [DX0001]
R5F10BCCLLA [DX0001]
R5F10BCDKLA [DX0001]
R5F10BCDYLA [DX0001]
R5F10BCELLA [DX0001]
R5F10BCFKLA [DX0001]
R5F10BCFYLA [DX0001]
R5F10BCGLLA [DX0001]
R5F10BCHKLA [DX0001]
R5F10BCHYLA [DX0001]
R5F10BCKLLA [DX0001]
R5F10BCLKLA [DX0001]
R5F10BCLYLA [DX0001]
R5F10BE8KNA [DX4017]
R5F10BE8YNA [DX4017]
R5F10BEALNA [DX4017]
R5F10BEBKNA [DX4017]
R5F10BEBYNA [DX4017]
R5F10BECLNA [DX4017]
R5F10BEDKNA [DX4017]
R5F10BEDYNA [DX4017]
R5F10BEELNA [DX4017]
R5F10BEFKNA [DX4017]
R5F10BEFYNA [DX4017]
R5F10BEGLNA [DX4017]
R5F10BEHKNA [DX4017]
R5F10BEHYNA [DX4017]
R5F10BEKLNA [DX4017]
R5F10BELKNA [DX4017]
R5F10BELYNA [DX4017]
R5F10BF8KFP [DX3002]
R5F10BF8YFP [DX3002]
R5F10BFALFP [DX3002]
R5F10BFBKFP [DX3002]
R5F10BFBYFP [DX3002]

R5F10BFCKFP [DX3002]
R5F10BFCLFP [DX3002]
R5F10BFCYFP [DX3002]
R5F10BFDKFP [DX3002]
R5F10BFDLFP [DX3002]
R5F10BFDYFP [DX3002]
R5F10BFEKFP [DX3002]
R5F10BFELFP [DX3002]
R5F10BFEYFP [DX3002]
R5F10BFFKFP [DX3002]
R5F10BFFLFP [DX3002]
R5F10BFFYFP [DX3002]
R5F10BFGKFP [DX3002]
R5F10BFGLFP [DX3002]
R5F10BFGYFP [DX3002]
R5F10BFHKFP [DX3002]
R5F10BFHLFP [DX3002]
R5F10BFHYFP [DX3002]
R5F10BFKKFP [DX3002]
R5F10BFKLFP [DX3002]
R5F10BFKYFP [DX3002]
R5F10BFLKFP [DX3002]
R5F10BFLLFP [DX3002]
R5F10BFLYFP [DX3002]
R5F10BFYYFP [DX3002]
R5F10BG8KFB [DX3007]
R5F10BG8KNA [DX4021]
R5F10BG8LFB [DX3007]
R5F10BG8LNA [DX4021]
R5F10BG8YFB [DX3007]
R5F10BG8YNA [DX4021]
R5F10BGAKFB [DX3007]
R5F10BGAKNA [DX4021]
R5F10BGALFB [DX3007]
R5F10BGALNA [DX4021]
R5F10BGAYFB [DX3007]
R5F10BGAYNA [DX4021]
R5F10BGBKFB [DX3007]
R5F10BGBKNA [DX4021]
R5F10BGBLFB [DX3007]
R5F10BGBLNA [DX4021]
R5F10BGBYFB [DX3007]
R5F10BGBYNA [DX4021]
R5F10BGCKFB [DX3007]
R5F10BGCKNA [DX4021]
R5F10BGCLFB [DX3007]
R5F10BGCLNA [DX4021]
R5F10BGCYFB [DX3007]
R5F10BGCYNA [DX4021]
R5F10BGDKFB [DX3007]
R5F10BGDKNA [DX4021]
R5F10BGDLFB [DX3007]
R5F10BGDLNA [DX4021]
R5F10BGDYFB [DX3007]
R5F10BGDYNA [DX4021]
R5F10BGEKFB [DX3007]
R5F10BGEKNA [DX4021]
R5F10BGELFB [DX3007]
R5F10BGELNA [DX4021]
R5F10BGEYFB [DX3007]
R5F10BGEYNA [DX4021]
R5F10BGFKFB [DX3007]
R5F10BGFKNA [DX4021]
R5F10BGFLFB [DX3007]
R5F10BGFLNA [DX4021]
R5F10BGFYFB [DX3007]
R5F10BGFYNA [DX4021]
R5F10BGGKFB [DX3007]
R5F10BGGKNA [DX4021]
R5F10BGGLFB [DX3007]
R5F10BGGLNA [DX4021]
R5F10BGGYFB [DX3007]
R5F10BGGYNA [DX4021]
R5F10BGHKFB [DX3007]
R5F10BGHKNA [DX4021]
R5F10BGHLFB [DX3007]
R5F10BGHLNA [DX4021]
R5F10BGHYFB [DX3007]
R5F10BGHYNA [DX4021]
R5F10BGKKFB [DX3007]
R5F10BGKKNA [DX4021]
R5F10BGKLFB [DX3007]
R5F10BGKLNA [DX4021]
R5F10BGKYFB [DX3007]
R5F10BGKYNA [DX4021]
R5F10BGLKFB [DX3007]
R5F10BGLKNA [DX4021]
R5F10BGLLFB [DX3007]
R5F10BGLLNA [DX4021]
R5F10BGLYFB [DX3007]
R5F10BGLYNA [DX4021]
R5F10BGYYFB [DX3007]
R5F10BGYYNA [DX4021]
R5F10BL8KFB [DX3011]
R5F10BL8LFB [DX3011]
R5F10BL8YFB [DX3011]

R5F10BLAKFB [DX3011]
R5F10BLALFB [DX3011]
R5F10BLAYFB [DX3011]
R5F10BLBKFB [DX3011]
R5F10BLBLFB [DX3011]
R5F10BLBYFB [DX3011]
R5F10BLCKFB [DX3011]
R5F10BLCLFB [DX3011]
R5F10BLCYFB [DX3011]
R5F10BLDKFB [DX3011]
R5F10BLDLFB [DX3011]
R5F10BLDYFB [DX3011]
R5F10BLEKFB [DX3011]
R5F10BLELFB [DX3011]
R5F10BLEYFB [DX3011]
R5F10BLFKFB [DX3011]
R5F10BLFLFB [DX3011]
R5F10BLFYFB [DX3011]
R5F10BLGKFB [DX3011]
R5F10BLGLFB [DX3011]
R5F10BLGYFB [DX3011]
R5F10BLHKFB [DX3011]
R5F10BLHLFB [DX3011]
R5F10BLHYFB [DX3011]
R5F10BLKKFB [DX3011]
R5F10BLKLFB [DX3011]
R5F10BLKYFB [DX3011]
R5F10BLLKFB [DX3011]
R5F10BLLLFB [DX3011]
R5F10BLLYFB [DX3011]
R5F10BLYYFB [DX3011]
R5F10C6AJSP [DX1026]
R5F10C6ALSP [DX1026]
R5F10C6CJSP [DX1026]
R5F10C6CLSP [DX1026]
R5F10C6DJSP [DX1026]
R5F10C6DLSP [DX1026]
R5F10C6EJSP [DX1026]
R5F10C6ELSP [DX1026]
R5F10C6FJSP [DX1026]
R5F10C6FLSP [DX1026]
R5F10C6GJSP [DX1026]
R5F10C6GLSP [DX1026]
R5F10C6HJSP [DX1026]
R5F10C6HLSP [DX1026]
R5F10C6JJSP [DX1026]
R5F10C6JLSP [DX1026]
R5F10C6KJSP [DX1026]
R5F10C6KLSP [DX1026]
R5F10C6LJSP [DX1026]
R5F10C6LLSP [DX1026]
R5F10C7AJNA [DX4012]
R5F10C7ALNA [DX4012]
R5F10C7CJNA [DX4012]
R5F10C7CLNA [DX4012]
R5F10C7DJNA [DX4012]
R5F10C7DLNA [DX4012]
R5F10C7EJNA [DX4012]
R5F10C7ELNA [DX4012]
R5F10C7FJNA [DX4012]
R5F10C7FLNA [DX4012]
R5F10C7GJNA [DX4012]
R5F10C7GLNA [DX4012]
R5F10C7HJNA [DX4012]
R5F10C7HLNA [DX4012]
R5F10C7JJNA [DX4012]
R5F10C7JLNA [DX4012]
R5F10C7KJNA [DX4012]
R5F10C7KLNA [DX4012]
R5F10C7LJNA [DX4012]
R5F10C7LLNA [DX4012]
R5F10C8AJLA [DX0001]
R5F10C8ALLA [DX0001]
R5F10C8CJLA [DX0001]
R5F10C8CLLA [DX0001]
R5F10C8DJLA [DX0001]
R5F10C8DLLA [DX0001]
R5F10C8EJLA [DX0001]
R5F10C8ELLA [DX0001]
R5F10C8FJLA [DX0001]
R5F10C8FLLA [DX0001]
R5F10C8GJLA [DX0001]
R5F10C8GLLA [DX0001]
R5F10C8HJLA [DX0001]
R5F10C8HLLA [DX0001]
R5F10C8JJLA [DX0001]
R5F10C8JLLA [DX0001]
R5F10C8KJLA [DX0001]
R5F10C8KLLA [DX0001]
R5F10C8LJLA [DX0001]
R5F10C8LLLA [DX0001]
R5F10CAAJSP [DX1087]
R5F10CAALSP [DX1087]
R5F10CACJSP [DX1087]
R5F10CACLSP [DX1087]
R5F10CADJSP [DX1087]

R5F10CADLSP [DX1087]
R5F10CAELSP [DX1087]
R5F10CAFLSP [DX1087]
R5F10CAGLSP [DX1087]
R5F10CAHLSP [DX1087]
R5F10CAJLSP [DX1087]
R5F10CAKLSP [DX1087]
R5F10CALLSP [DX1087]
R5F10CBALNA [DX4015]
R5F10CBCLNA [DX4015]
R5F10CBDLNA [DX4015]
R5F10CBELNA [DX4015]
R5F10CBFLNA [DX4015]
R5F10CBGLNA [DX4015]
R5F10CBHLNA [DX4015]
R5F10CBJLNA [DX4015]
R5F10CBKLNA [DX4015]
R5F10CBLLNA [DX4015]
R5F10CCALLA [DX0001]
R5F10CCCLLA [DX0001]
R5F10CCDLLA [DX0001]
R5F10CCELLA [DX0001]
R5F10CCFLLA [DX0001]
R5F10CCGLLA [DX0001]
R5F10CCHLLA [DX0001]
R5F10CCJLLA [DX0001]
R5F10CCKLLA [DX0001]
R5F10CCLLLA [DX0001]
R5F10CEALNA [DX4017]
R5F10CECLNA [DX4017]
R5F10CEDLNA [DX4017]
R5F10CEELNA [DX4017]
R5F10CEFLNA [DX4017]
R5F10CEGLNA [DX4017]
R5F10CEHLNA [DX4017]
R5F10CEJLNA [DX4017]
R5F10CEKLNA [DX4017]
R5F10CELLNA [DX4017]
R5F10CFALFP [DX3005]
R5F10CFCLFP [DX3005]
R5F10CFDLFP [DX3005]
R5F10CFELFP [DX3005]
R5F10CFFLFP [DX3005]
R5F10CFGLFP [DX3005]
R5F10CFHLFP [DX3005]
R5F10CFJLFP [DX3005]
R5F10CFKLFP [DX3005]
R5F10CFLLFP [DX3005]
R5F10CAEJSP [DX1087]
R5F10CAFJSP [DX1087]
R5F10CAGJSP [DX1087]
R5F10CAHJSP [DX1087]
R5F10CAJJSP [DX1087]
R5F10CAKJSP [DX1087]
R5F10CALJSP [DX1087]
R5F10CBAJNA [DX4015]
R5F10CBCJNA [DX4015]
R5F10CBDJNA [DX4015]
R5F10CBEJNA [DX4015]
R5F10CBFJNA [DX4015]
R5F10CBGJNA [DX4015]
R5F10CBHJNA [DX4015]
R5F10CBJJNA [DX4015]
R5F10CBKJNA [DX4015]
R5F10CBLJNA [DX4015]
R5F10CCAJLA [DX0001]
R5F10CCCJLA [DX0001]
R5F10CCDJLA [DX0001]
R5F10CCEJLA [DX0001]
R5F10CCFJLA [DX0001]
R5F10CCGJLA [DX0001]
R5F10CCHJLA [DX0001]
R5F10CCJJLA [DX0001]
R5F10CCKJLA [DX0001]
R5F10CCLJLA [DX0001]
R5F10CEAJNA [DX4017]
R5F10CECJNA [DX4017]
R5F10CEDJNA [DX4017]
R5F10CEEJNA [DX4017]
R5F10CEFJNA [DX4017]
R5F10CEGJNA [DX4017]
R5F10CEHJNA [DX4017]
R5F10CEJJNA [DX4017]
R5F10CEKJNA [DX4017]
R5F10CELJNA [DX4017]
R5F10CFAJFP [DX3005]
R5F10CFCJFP [DX3005]
R5F10CFDJFP [DX3005]
R5F10CFEJFP [DX3005]
R5F10CFFJFP [DX3005]
R5F10CFGJFP [DX3005]
R5F10CFHJFP [DX3005]
R5F10CFJJFP [DX3005]
R5F10CFKJFP [DX3005]
R5F10CFLJFP [DX3005]
R5F10CGAJFB [DX3007]

R5F10CGAJNA [DX4021]
R5F10CGALNA [DX4021]
R5F10CGCJNA [DX4021]
R5F10CGCLNA [DX4021]
R5F10CGDJNA [DX4021]
R5F10CGDLNA [DX4021]
R5F10CGEJNA [DX4021]
R5F10CGELNA [DX4021]
R5F10CGFJNA [DX4021]
R5F10CGFLNA [DX4021]
R5F10CGGJNA [DX4021]
R5F10CGGLNA [DX4021]
R5F10CGHJNA [DX4021]
R5F10CGHLNA [DX4021]
R5F10CGJJNA [DX4021]
R5F10CGJLNA [DX4021]
R5F10CGKJNA [DX4021]
R5F10CGKLNA [DX4021]
R5F10CGLJNA [DX4021]
R5F10CGLLNA [DX4021]
R5F10CJCLFA [DX3010]
R5F10CJDLFA [DX3010]
R5F10CJELFA [DX3010]
R5F10CJFLFA [DX3010]
R5F10CJGLFA [DX3010]
R5F10CJHLFA [DX3010]
R5F10CJJLFA [DX3010]
R5F10CJKLFA [DX3010]
R5F10CJLLFA [DX3010]
R5F10CLCJFA [DX3012]
R5F10CLCJFC [DX3085]
R5F10CLCLFA [DX3012]
R5F10CLCLFC [DX3085]
R5F10CLDJFA [DX3012]
R5F10CLDJFC [DX3085]
R5F10CLDLFA [DX3012]
R5F10CLDLFC [DX3085]
R5F10CLEJFA [DX3012]
R5F10CLEJFC [DX3085]
R5F10CLELFA [DX3012]
R5F10CLELFC [DX3085]
R5F10CLFJFA [DX3012]
R5F10CLFJFC [DX3085]
R5F10CLFLFA [DX3012]
R5F10CLFLFC [DX3085]
R5F10CLGJFA [DX3012]
R5F10CLGJFC [DX3085]
R5F10CLGLFA [DX3012]
R5F10CGALFB [DX3007]
R5F10CGCJFB [DX3007]
R5F10CGCLFB [DX3007]
R5F10CGDJFB [DX3007]
R5F10CGDLFB [DX3007]
R5F10CGEJFB [DX3007]
R5F10CGELFB [DX3007]
R5F10CGFJFB [DX3007]
R5F10CGFLFB [DX3007]
R5F10CGGJFB [DX3007]
R5F10CGGLFB [DX3007]
R5F10CGHJFB [DX3007]
R5F10CGHLFB [DX3007]
R5F10CGJJFB [DX3007]
R5F10CGJLFB [DX3007]
R5F10CGKJFB [DX3007]
R5F10CGKLFB [DX3007]
R5F10CGLJFB [DX3007]
R5F10CGLLFB [DX3007]
R5F10CJCJFA [DX3010]
R5F10CJDJFA [DX3010]
R5F10CJEJFA [DX3010]
R5F10CJFJFA [DX3010]
R5F10CJGJFA [DX3010]
R5F10CJHJFA [DX3010]
R5F10CJJJFA [DX3010]
R5F10CJKJFA [DX3010]
R5F10CJLJFA [DX3010]
R5F10CLCJBG [DX0001]
R5F10CLCJFB [DX3011]
R5F10CLCLBG [DX0001]
R5F10CLCLFB [DX3011]
R5F10CLDJBG [DX0001]
R5F10CLDJFB [DX3011]
R5F10CLDLBG [DX0001]
R5F10CLDLFB [DX3011]
R5F10CLEJBG [DX0001]
R5F10CLEJFB [DX3011]
R5F10CLELBG [DX0001]
R5F10CLELFB [DX3011]
R5F10CLFJBG [DX0001]
R5F10CLFJFB [DX3011]
R5F10CLFLBG [DX0001]
R5F10CLFLFB [DX3011]
R5F10CLGJBG [DX0001]
R5F10CLGJFB [DX3011]
R5F10CLGLBG [DX0001]
R5F10CLGLFB [DX3011]

R5F10CLGLFC [DX3085]
R5F10CLHJFA [DX3012]
R5F10CLHJFC [DX3085]
R5F10CLHLFA [DX3012]
R5F10CLHLFC [DX3085]
R5F10CLJJFA [DX3012]
R5F10CLJJFC [DX3085]
R5F10CLJLFA [DX3012]
R5F10CLJLFC [DX3085]
R5F10CLKJFA [DX3012]
R5F10CLKJFC [DX3085]
R5F10CLKLFA [DX3012]
R5F10CLKLFC [DX3085]
R5F10CLLJFA [DX3012]
R5F10CLLJFC [DX3085]
R5F10CLLLFA [DX3012]
R5F10CLLLFC [DX3085]
R5F10CMCJFB [DX3016]
R5F10CMCLFB [DX3016]
R5F10CMDJFB [DX3016]
R5F10CMDLFB [DX3016]
R5F10CMEJFB [DX3016]
R5F10CMELFB [DX3016]
R5F10CMFJFB [DX3016]
R5F10CMFLFB [DX3016]
R5F10CMGJFB [DX3016]
R5F10CMGLFB [DX3016]
R5F10CMHJFB [DX3016]
R5F10CMHLFB [DX3016]
R5F10CMJJFB [DX3016]
R5F10CMJLFB [DX3016]
R5F10CMKJFB [DX3016]
R5F10CMKLFB [DX3016]
R5F10CMLJFB [DX3016]
R5F10CMLLFB [DX3016]
R5F10CPCJFB [DX3021]
R5F10CPCLFB [DX3021]
R5F10CPDJFB [DX3021]
R5F10CPDLFB [DX3021]
R5F10CPEJFB [DX3021]
R5F10CPELFB [DX3021]
R5F10CPFJFB [DX3021]
R5F10CPFLFB [DX3021]
R5F10CPGJFB [DX3021]
R5F10CPGLFB [DX3021]
R5F10CPHJFB [DX3021]
R5F10CPHLFB [DX3021]
R5F10CPJJFB [DX3021]
R5F10CLHJBG [DX0001]
R5F10CLHJFB [DX3011]
R5F10CLHLBG [DX0001]
R5F10CLHLFB [DX3011]
R5F10CLJJBG [DX0001]
R5F10CLJJFB [DX3011]
R5F10CLJLBG [DX0001]
R5F10CLJLFB [DX3011]
R5F10CLKJBG [DX0001]
R5F10CLKJFB [DX3011]
R5F10CLKLBG [DX0001]
R5F10CLKLFB [DX3011]
R5F10CLLJBG [DX0001]
R5F10CLLJFB [DX3011]
R5F10CLLLBG [DX0001]
R5F10CLLLFB [DX3011]
R5F10CMCJFA [DX3018]
R5F10CMCLFA [DX3017]
R5F10CMDJFA [DX3018]
R5F10CMDLFA [DX3017]
R5F10CMEJFA [DX3018]
R5F10CMELFA [DX3017]
R5F10CMFJFA [DX3018]
R5F10CMFLFA [DX3017]
R5F10CMGJFA [DX3018]
R5F10CMGLFA [DX3017]
R5F10CMHJFA [DX3018]
R5F10CMHLFA [DX3017]
R5F10CMJJFA [DX3018]
R5F10CMJLFA [DX3017]
R5F10CMKJFA [DX3018]
R5F10CMKLFA [DX3017]
R5F10CMLJFA [DX3018]
R5F10CMLLFA [DX3017]
R5F10CPCJFA [DX3062]
R5F10CPCLFA [DX3062]
R5F10CPDJFA [DX3062]
R5F10CPDLFA [DX3062]
R5F10CPEJFA [DX3062]
R5F10CPELFA [DX3062]
R5F10CPFJFA [DX3062]
R5F10CPFLFA [DX3062]
R5F10CPGJFA [DX3062]
R5F10CPGLFA [DX3062]
R5F10CPHJFA [DX3062]
R5F10CPHLFA [DX3062]
R5F10CPJJFA [DX3062]
R5F10CPJLFA [DX3062]

R5F10CPJLFB [DX3021]
R5F10CPKJFB [DX3021]
R5F10CPKLFB [DX3021]
R5F10CPLJFB [DX3021]
R5F10CPLLFB [DX3021]
R5F10CSCLFB [DX3031]
R5F10CSDLFB [DX3031]
R5F10CSELFB [DX3031]
R5F10CSFLFB [DX3031]
R5F10CSGLFB [DX3031]
R5F10CSHLFB [DX3031]
R5F10CSJLFB [DX3031]
R5F10CSKLFB [DX3031]
R5F10CSLLFB [DX3031]
R5F10D6ALSP [DX1026]
R5F10D6CLSP [DX1026]
R5F10D6DLSP [DX1026]
R5F10D6ELSP [DX1026]
R5F10D6FLSP [DX1026]
R5F10D6GLSP [DX1026]
R5F10D6HLSP [DX1026]
R5F10D6JLSP [DX1026]
R5F10D6KLSP [DX1026]
R5F10D6LLSP [DX1026]
R5F10D7ALNA [DX4012]
R5F10D7CLNA [DX4012]
R5F10D7DLNA [DX4012]
R5F10D7ELNA [DX4012]
R5F10D7FLNA [DX4012]
R5F10D7GLNA [DX4012]
R5F10D7HLNA [DX4012]
R5F10D7JLNA [DX4012]
R5F10D7KLNA [DX4012]
R5F10D7LLNA [DX4012]
R5F10D8ALLA [DX0001]
R5F10D8CLLA [DX0001]
R5F10D8DLLA [DX0001]
R5F10D8ELLA [DX0001]
R5F10D8FLLA [DX0001]
R5F10D8GLLA [DX0001]
R5F10D8HLLA [DX0001]
R5F10D8JLLA [DX0001]
R5F10D8KLLA [DX0001]
R5F10D8LLLA [DX0001]
R5F10DAALSP [DX1087]
R5F10DACLSP [DX1087]
R5F10DADLSP [DX1087]
R5F10DAELSP [DX1087]
R5F10CPKJFA [DX3062]
R5F10CPKLFA [DX3062]
R5F10CPLJFA [DX3062]
R5F10CPLLFA [DX3062]
R5F10CSCJFB [DX3031]
R5F10CSDJFB [DX3031]
R5F10CSEJFB [DX3031]
R5F10CSFJFB [DX3031]
R5F10CSGJFB [DX3031]
R5F10CSHJFB [DX3031]
R5F10CSJJFB [DX3031]
R5F10CSKJFB [DX3031]
R5F10CSLJFB [DX3031]
R5F10D6AJSP [DX1026]
R5F10D6CJSP [DX1026]
R5F10D6DJSP [DX1026]
R5F10D6EJSP [DX1026]
R5F10D6FJSP [DX1026]
R5F10D6GJSP [DX1026]
R5F10D6HJSP [DX1026]
R5F10D6JJSP [DX1026]
R5F10D6KJSP [DX1026]
R5F10D6LJSP [DX1026]
R5F10D7AJNA [DX4012]
R5F10D7CJNA [DX4012]
R5F10D7DJNA [DX4012]
R5F10D7EJNA [DX4012]
R5F10D7FJNA [DX4012]
R5F10D7GJNA [DX4012]
R5F10D7HJNA [DX4012]
R5F10D7JJNA [DX4012]
R5F10D7KJNA [DX4012]
R5F10D7LJNA [DX4012]
R5F10D8AJLA [DX0001]
R5F10D8CJLA [DX0001]
R5F10D8DJLA [DX0001]
R5F10D8EJLA [DX0001]
R5F10D8FJLA [DX0001]
R5F10D8GJLA [DX0001]
R5F10D8HJLA [DX0001]
R5F10D8JJLA [DX0001]
R5F10D8KJLA [DX0001]
R5F10D8LJLA [DX0001]
R5F10DAAJSP [DX1087]
R5F10DACJSP [DX1087]
R5F10DADJSP [DX1087]
R5F10DAEJSP [DX1087]
R5F10DAFJSP [DX1087]

R5F10DAFLSP [DX1087]
R5F10DAGLSP [DX1087]
R5F10DAHLSP [DX1087]
R5F10DAJLSP [DX1087]
R5F10DAKLSP [DX1087]
R5F10DALLSP [DX1087]
R5F10DBALNA [DX4015]
R5F10DBCLNA [DX4015]
R5F10DBDLNA [DX4015]
R5F10DBELNA [DX4015]
R5F10DBFLNA [DX4015]
R5F10DBGLNA [DX4015]
R5F10DBHLNA [DX4015]
R5F10DBJLNA [DX4015]
R5F10DBKLNA [DX4015]
R5F10DBLLNA [DX4015]
R5F10DCALLA [DX0001]
R5F10DCCLLA [DX0001]
R5F10DCDLLA [DX0001]
R5F10DCELLA [DX0001]
R5F10DCFLLA [DX0001]
R5F10DCGLLA [DX0001]
R5F10DCHLLA [DX0001]
R5F10DCJLLA [DX0001]
R5F10DCKLLA [DX0001]
R5F10DCLLLA [DX0001]
R5F10DEALNA [DX4017]
R5F10DECLNA [DX4017]
R5F10DEDLNA [DX4017]
R5F10DEELNA [DX4017]
R5F10DEFLNA [DX4017]
R5F10DEGLNA [DX4017]
R5F10DEHLNA [DX4017]
R5F10DEJLNA [DX4017]
R5F10DEKLNA [DX4017]
R5F10DELLNA [DX4017]
R5F10DFALFP [DX3005]
R5F10DFCLFP [DX3005]
R5F10DFDLFP [DX3005]
R5F10DFELFP [DX3005]
R5F10DFFLFP [DX3005]
R5F10DFGLFP [DX3005]
R5F10DFHLFP [DX3005]
R5F10DFJLFP [DX3005]
R5F10DFKLFP [DX3005]
R5F10DFLLFP [DX3005]
R5F10DGAJNA [DX4021]
R5F10DGALNA [DX4021]
R5F10DAGJSP [DX1087]
R5F10DAHJSP [DX1087]
R5F10DAJJSP [DX1087]
R5F10DAKJSP [DX1087]
R5F10DALJSP [DX1087]
R5F10DBAJNA [DX4015]
R5F10DBCJNA [DX4015]
R5F10DBDJNA [DX4015]
R5F10DBEJNA [DX4015]
R5F10DBFJNA [DX4015]
R5F10DBGJNA [DX4015]
R5F10DBHJNA [DX4015]
R5F10DBJJNA [DX4015]
R5F10DBKJNA [DX4015]
R5F10DBLJNA [DX4015]
R5F10DCAJLA [DX0001]
R5F10DCCJLA [DX0001]
R5F10DCDJLA [DX0001]
R5F10DCEJLA [DX0001]
R5F10DCFJLA [DX0001]
R5F10DCGJLA [DX0001]
R5F10DCHJLA [DX0001]
R5F10DCJJLA [DX0001]
R5F10DCKJLA [DX0001]
R5F10DCLJLA [DX0001]
R5F10DEAJNA [DX4017]
R5F10DECJNA [DX4017]
R5F10DEDJNA [DX4017]
R5F10DEEJNA [DX4017]
R5F10DEFJNA [DX4017]
R5F10DEGJNA [DX4017]
R5F10DEHJNA [DX4017]
R5F10DEJJNA [DX4017]
R5F10DEKJNA [DX4017]
R5F10DELJNA [DX4017]
R5F10DFAJFP [DX3005]
R5F10DFCJFP [DX3005]
R5F10DFDJFP [DX3005]
R5F10DFEJFP [DX3005]
R5F10DFFJFP [DX3005]
R5F10DFGJFP [DX3005]
R5F10DFHJFP [DX3005]
R5F10DFJJFP [DX3005]
R5F10DFKJFP [DX3005]
R5F10DFLJFP [DX3005]
R5F10DGAJFB [DX3007]
R5F10DGALFB [DX3007]
R5F10DGCJFB [DX3007]

R5F10DGCJNA [DX4021]
R5F10DGCLNA [DX4021]
R5F10DGDJNA [DX4021]
R5F10DGDLNA [DX4021]
R5F10DGEJNA [DX4021]
R5F10DGELNA [DX4021]
R5F10DGFJNA [DX4021]
R5F10DGFLNA [DX4021]
R5F10DGGJNA [DX4021]
R5F10DGGLNA [DX4021]
R5F10DGHJNA [DX4021]
R5F10DGHLNA [DX4021]
R5F10DGJJNA [DX4021]
R5F10DGJLNA [DX4021]
R5F10DGKJNA [DX4021]
R5F10DGKLNA [DX4021]
R5F10DGLJNA [DX4021]
R5F10DGLLNA [DX4021]
R5F10DJCLFA [DX3010]
R5F10DJDLFA [DX3010]
R5F10DJELFA [DX3010]
R5F10DJFLFA [DX3010]
R5F10DJGLFA [DX3010]
R5F10DJHLFA [DX3010]
R5F10DJJLFA [DX3010]
R5F10DJKLFA [DX3010]
R5F10DJLLFA [DX3010]
R5F10DLCJFA [DX3012]
R5F10DLCJFC [DX3085]
R5F10DLCLFA [DX3012]
R5F10DLCLFC [DX3085]
R5F10DLDJFA [DX3012]
R5F10DLDJFC [DX3085]
R5F10DLDLFA [DX3012]
R5F10DLDLFC [DX3085]
R5F10DLEJFA [DX3012]
R5F10DLEJFC [DX3085]
R5F10DLELFA [DX3012]
R5F10DLELFC [DX3085]
R5F10DLFJFA [DX3012]
R5F10DLFJFC [DX3085]
R5F10DLFLFA [DX3012]
R5F10DLFLFC [DX3085]
R5F10DLGJFA [DX3012]
R5F10DLGJFC [DX3085]
R5F10DLGLFA [DX3012]
R5F10DLGLFC [DX3085]
R5F10DLHJFA [DX3012]
R5F10DGCLFB [DX3007]
R5F10DGDJFB [DX3007]
R5F10DGDLFB [DX3007]
R5F10DGEJFB [DX3007]
R5F10DGELFB [DX3007]
R5F10DGFJFB [DX3007]
R5F10DGFLFB [DX3007]
R5F10DGGJFB [DX3007]
R5F10DGGLFB [DX3007]
R5F10DGHJFB [DX3007]
R5F10DGHLFB [DX3007]
R5F10DGJJFB [DX3007]
R5F10DGJLFB [DX3007]
R5F10DGKJFB [DX3007]
R5F10DGKLFB [DX3007]
R5F10DGLJFB [DX3007]
R5F10DGLLFB [DX3007]
R5F10DJCJFA [DX3010]
R5F10DJDJFA [DX3010]
R5F10DJEJFA [DX3010]
R5F10DJFJFA [DX3010]
R5F10DJGJFA [DX3010]
R5F10DJHJFA [DX3010]
R5F10DJJJFA [DX3010]
R5F10DJKJFA [DX3010]
R5F10DJLJFA [DX3010]
R5F10DLCJBG [DX0001]
R5F10DLCJFB [DX3011]
R5F10DLCLBG [DX0001]
R5F10DLCLFB [DX3011]
R5F10DLDJBG [DX0001]
R5F10DLDJFB [DX3011]
R5F10DLDLBG [DX0001]
R5F10DLDLFB [DX3011]
R5F10DLEJBG [DX0001]
R5F10DLEJFB [DX3011]
R5F10DLELBG [DX0001]
R5F10DLELFB [DX3011]
R5F10DLFJBG [DX0001]
R5F10DLFJFB [DX3011]
R5F10DLFLBG [DX0001]
R5F10DLFLFB [DX3011]
R5F10DLGJBG [DX0001]
R5F10DLGJFB [DX3011]
R5F10DLGLBG [DX0001]
R5F10DLGLFB [DX3011]
R5F10DLHJBG [DX0001]
R5F10DLHJFB [DX3011]

R5F10DLHJFC [DX3085]
R5F10DLHLFA [DX3012]
R5F10DLHLFC [DX3085]
R5F10DLJJFA [DX3012]
R5F10DLJJFC [DX3085]
R5F10DLJLFA [DX3012]
R5F10DLJLFC [DX3085]
R5F10DLKJFA [DX3012]
R5F10DLKJFC [DX3085]
R5F10DLKLFA [DX3012]
R5F10DLKLFC [DX3085]
R5F10DLLJFA [DX3012]
R5F10DLLJFC [DX3085]
R5F10DLLLFA [DX3012]
R5F10DLLLFC [DX3085]
R5F10DMCJFB [DX3016]
R5F10DMCLFB [DX3016]
R5F10DMDJFB [DX3016]
R5F10DMDLFB [DX3016]
R5F10DMEJFB [DX3016]
R5F10DMELFB [DX3016]
R5F10DMFJFB [DX3016]
R5F10DMFLFB [DX3016]
R5F10DMGJFB [DX3016]
R5F10DMGLFB [DX3016]
R5F10DMHJFB [DX3016]
R5F10DMHLFB [DX3016]
R5F10DMJJFB [DX3016]
R5F10DMJLFB [DX3016]
R5F10DMKJFB [DX3016]
R5F10DMKLFB [DX3016]
R5F10DMLJFB [DX3016]
R5F10DMLLFB [DX3016]
R5F10DPCJFB [DX3021]
R5F10DPCLFB [DX3021]
R5F10DPDJFB [DX3021]
R5F10DPDLFB [DX3021]
R5F10DPEJFB [DX3021]
R5F10DPELFB [DX3021]
R5F10DPFJFB [DX3021]
R5F10DPFLFB [DX3021]
R5F10DPGJFB [DX3021]
R5F10DPGLFB [DX3021]
R5F10DPHJFB [DX3021]
R5F10DPHLFB [DX3021]
R5F10DPJJFB [DX3021]
R5F10DPJLFB [DX3021]
R5F10DPKJFB [DX3021]
R5F10DLHLBG [DX0001]
R5F10DLHLFB [DX3011]
R5F10DLJJBG [DX0001]
R5F10DLJJFB [DX3011]
R5F10DLJLBG [DX0001]
R5F10DLJLFB [DX3011]
R5F10DLKJBG [DX0001]
R5F10DLKJFB [DX3011]
R5F10DLKLBG [DX0001]
R5F10DLKLFB [DX3011]
R5F10DLLJBG [DX0001]
R5F10DLLJFB [DX3011]
R5F10DLLLBG [DX0001]
R5F10DLLLFB [DX3011]
R5F10DMCJFA [DX3017]
R5F10DMCLFA [DX3017]
R5F10DMDJFA [DX3017]
R5F10DMDLFA [DX3017]
R5F10DMEJFA [DX3017]
R5F10DMELFA [DX3017]
R5F10DMFJFA [DX3017]
R5F10DMFLFA [DX3017]
R5F10DMGJFA [DX3017]
R5F10DMGLFA [DX3017]
R5F10DMHJFA [DX3017]
R5F10DMHLFA [DX3017]
R5F10DMJJFA [DX3017]
R5F10DMJLFA [DX3017]
R5F10DMKJFA [DX3017]
R5F10DMKLFA [DX3017]
R5F10DMLJFA [DX3017]
R5F10DMLLFA [DX3017]
R5F10DPCJFA [DX3062]
R5F10DPCLFA [DX3062]
R5F10DPDJFA [DX3062]
R5F10DPDLFA [DX3062]
R5F10DPEJFA [DX3062]
R5F10DPELFA [DX3062]
R5F10DPFJFA [DX3062]
R5F10DPFLFA [DX3062]
R5F10DPGJFA [DX3062]
R5F10DPGLFA [DX3062]
R5F10DPHJFA [DX3062]
R5F10DPHLFA [DX3062]
R5F10DPJJFA [DX3062]
R5F10DPJLFA [DX3062]
R5F10DPKJFA [DX3062]
R5F10DPKLFA [DX3062]

R5F10DPKLFB [DX3021]
R5F10DPLJFB [DX3021]
R5F10DPLLFB [DX3021]
R5F10DSCLFB [DX3031]
R5F10DSDLFB [DX3031]
R5F10DSELFB [DX3031]
R5F10DSFLFB [DX3031]
R5F10DSGLFB [DX3031]
R5F10DSHLFB [DX3031]
R5F10DSJLFB [DX3031]
R5F10DSKLFB [DX3031]
R5F10DSLLFB [DX3031]
R5F10WLAAFB [DX3011]
R5F10WLAGFB [DX3011]
R5F10WLBAFB [DX3011]
R5F10WLBGFB [DX3011]
R5F10WLCAFB [DX3011]
R5F10WLCGFB [DX3011]
R5F10WLDAFB [DX3011]
R5F10WLDGFB [DX3011]
R5F10WLEAFB [DX3011]
R5F10WLEGFB [DX3011]
R5F10WLFAFB [DX3011]
R5F10WLFGFB [DX3011]
R5F10WLGAFB [DX3011]
R5F10WLGGFB [DX3011]
R5F10WMAAFB [DX3016]
R5F10WMAGFB [DX3016]
R5F10WMBAFB [DX3016]
R5F10WMBGFB [DX3016]
R5F10WMCAFB [DX3016]
R5F10WMCGFB [DX3016]
R5F10WMDAFB [DX3016]
R5F10WMDGFB [DX3016]
R5F10WMEAFB [DX3016]
R5F10WMEGFB [DX3016]
R5F10WMFAFB [DX3016]
R5F10WMFGFB [DX3016]
R5F10WMGAFB [DX3016]
R5F10WMGGFB [DX3016]
R5F10Y16ASP [DX1001]
R5F10Y44ASP [DX1001]
R5F10Y47ASP [DX1001]
R5F21102FP@TQFP32 [DX3001]
R5F21103FP@TQFP32 [DX3001]
R5F21104FP@TQFP32 [DX3001]
R5F21112FP@TQFP32 [DX3001]
R5F21113FP@TQFP32 [DX3001]
R5F10DPLJFA [DX3062]
R5F10DPLLFA [DX3062]
R5F10DSCJFB [DX3031]
R5F10DSDJFB [DX3031]
R5F10DSEJFB [DX3031]
R5F10DSFJFB [DX3031]
R5F10DSGJFB [DX3031]
R5F10DSHJFB [DX3031]
R5F10DSJJFB [DX3031]
R5F10DSKJFB [DX3031]
R5F10DSLJFB [DX3031]
R5F10WLAAFA [DX3012]
R5F10WLAGFA [DX3012]
R5F10WLBAFA [DX3012]
R5F10WLBGFA [DX3012]
R5F10WLCAFA [DX3012]
R5F10WLCGFA [DX3012]
R5F10WLDAFA [DX3012]
R5F10WLDGFA [DX3012]
R5F10WLEAFA [DX3012]
R5F10WLEGFA [DX3012]
R5F10WLFAFA [DX3012]
R5F10WLFGFA [DX3012]
R5F10WLGAFA [DX3012]
R5F10WLGGFA [DX3012]
R5F10WMAAFA [DX3017]
R5F10WMAGFA [DX3017]
R5F10WMBAFA [DX3017]
R5F10WMBGFA [DX3017]
R5F10WMCAFA [DX3017]
R5F10WMCGFA [DX3017]
R5F10WMDAFA [DX3017]
R5F10WMDGFA [DX3017]
R5F10WMEAFA [DX3017]
R5F10WMEGFA [DX3017]
R5F10WMFAFA [DX3017]
R5F10WMFGFA [DX3017]
R5F10WMGAFA [DX3017]
R5F10WMGGFA [DX3017]
R5F10Y14ASP [DX1001]
R5F10Y17ASP [DX1001]
R5F10Y46ASP [DX1001]
R5F21102DFP@TQFP32 [DX3001]
R5F21103DFP@TQFP32 [DX3001]
R5F21104DFP@TQFP32 [DX3001]
R5F21112DFP@TQFP32 [DX3001]
R5F21113DFP@TQFP32 [DX3001]
R5F21114DFP@TQFP32 [DX3001]

R5F21114FP@TQFP32 [DX3001]
R5F21122FP@TQFP32 [DX3001]
R5F21123FP@TQFP32 [DX3001]
R5F21124FP@TQFP32 [DX3001]
R5F21132FP@TQFP32 [DX3001]
R5F21133FP@TQFP32 [DX3001]
R5F21134FP@TQFP32 [DX3001]
R5F21122DFP@TQFP32 [DX3001]
R5F21123DFP@TQFP32 [DX3001]
R5F21124DFP@TQFP32 [DX3001]
R5F21132DFP@TQFP32 [DX3001]
R5F21133DFP@TQFP32 [DX3001]
R5F21134DFP@TQFP32 [DX3001]
R5F21142DSP@TSSOP20 [DX1000]
R5F21142DSP@TSSOP20(single ISP) [DX0001]
R5F21142DSP@TSSOP20(single wire) [DX1000]
R5F21142DSP@TSSOP20(UART ISP) [DX0001]
R5F21142DSP@TSSOP20(UART mode) [DX1000]
R5F21142SP@TSSOP20 [DX1000]
R5F21142SP@TSSOP20(single ISP) [DX0001]
R5F21142SP@TSSOP20(single wire) [DX1000]
R5F21142SP@TSSOP20(UART ISP) [DX0001]
R5F21142SP@TSSOP20(UART mode) [DX1000]
R5F21143DSP@TSSOP20 [DX1000]
R5F21143DSP@TSSOP20(single ISP) [DX0001]
R5F21143DSP@TSSOP20(single wire) [DX1000]
R5F21143DSP@TSSOP20(UART ISP) [DX0001]
R5F21143DSP@TSSOP20(UART mode) [DX1000]
R5F21143SP@TSSOP20 [DX1000]
R5F21143SP@TSSOP20(single ISP) [DX0001]
R5F21143SP@TSSOP20(single wire) [DX1000]
R5F21143SP@TSSOP20(UART ISP) [DX0001]
R5F21143SP@TSSOP20(UART mode) [DX1000]
R5F21144DSP@TSSOP20 [DX1000]
R5F21144DSP@TSSOP20(single ISP) [DX0001]
R5F21144DSP@TSSOP20(single wire) [DX1000]
R5F21144DSP@TSSOP20(UART ISP) [DX0001]
R5F21144DSP@TSSOP20(UART mode) [DX1000]
R5F21144SP@TSSOP20 [DX1000]
R5F21144SP@TSSOP20(single ISP) [DX0001]
R5F21144SP@TSSOP20(single wire) [DX1000]
R5F21144SP@TSSOP20(UART ISP) [DX0001]
R5F21144SP@TSSOP20(UART mode) [DX1000]
R5F21152DSP@TSSOP20 [DX1000]
R5F21152DSP@TSSOP20(single ISP) [DX0001]
R5F21152DSP@TSSOP20(single wire) [DX1000]
R5F21152DSP@TSSOP20(UART ISP) [DX0001]
R5F21152DSP@TSSOP20(UART mode) [DX1000]
R5F21152SP@TSSOP20 [DX1000]
R5F21152SP@TSSOP20(single ISP) [DX0001]
R5F21152SP@TSSOP20(single wire) [DX1000]
R5F21152SP@TSSOP20(UART ISP) [DX0001]
R5F21152SP@TSSOP20(UART mode) [DX1000]
R5F21153DSP@TSSOP20 [DX1000]
R5F21153DSP@TSSOP20(single ISP) [DX0001]

R5F21153DSP@TSSOP20(single wire) [DX1000]
R5F21153DSP@TSSOP20(UART ISP) [DX0001]
R5F21153DSP@TSSOP20(UART mode) [DX1000]
R5F21153SP@TSSOP20 [DX1000]
R5F21153SP@TSSOP20(single ISP) [DX0001]
R5F21153SP@TSSOP20(single wire) [DX1000]
R5F21153SP@TSSOP20(UART ISP) [DX0001]
R5F21153SP@TSSOP20(UART mode) [DX1000]
R5F21154DSP@TSSOP20 [DX1000]
R5F21154DSP@TSSOP20(single ISP) [DX0001]
R5F21154DSP@TSSOP20(single wire) [DX1000]
R5F21154DSP@TSSOP20(UART ISP) [DX0001]
R5F21154DSP@TSSOP20(UART mode) [DX1000]
R5F21154SP@TSSOP20 [DX1000]
R5F21154SP@TSSOP20(single ISP) [DX0001]
R5F21154SP@TSSOP20(single wire) [DX1000]
R5F21154SP@TSSOP20(UART ISP) [DX0001]
R5F21154SP@TSSOP20(UART mode) [DX1000]
R5F21162DSP@TSSOP20 [DX1000]
R5F21162DSP@TSSOP20(single ISP) [DX0001]
R5F21162DSP@TSSOP20(single wire) [DX1000]
R5F21162DSP@TSSOP20(UART ISP) [DX0001]
R5F21162DSP@TSSOP20(UART mode) [DX1000]
R5F21162SP@TSSOP20 [DX1000]
R5F21162SP@TSSOP20(single ISP) [DX0001]
R5F21162SP@TSSOP20(single wire) [DX1000]
R5F21162SP@TSSOP20(UART ISP) [DX0001]
R5F21162SP@TSSOP20(UART mode) [DX1000]
R5F21163DSP@TSSOP20 [DX1000]
R5F21163DSP@TSSOP20(single ISP) [DX0001]
R5F21163DSP@TSSOP20(single wire) [DX1000]
R5F21163DSP@TSSOP20(UART ISP) [DX0001]
R5F21163DSP@TSSOP20(UART mode) [DX1000]
R5F21163SP@TSSOP20 [DX1000]
R5F21163SP@TSSOP20(single ISP) [DX0001]
R5F21163SP@TSSOP20(single wire) [DX1000]
R5F21163SP@TSSOP20(UART ISP) [DX0001]
R5F21163SP@TSSOP20(UART mode) [DX1000]
R5F21164DSP@TSSOP20 [DX1000]
R5F21164DSP@TSSOP20(single ISP) [DX0001]
R5F21164DSP@TSSOP20(single wire) [DX1000]
R5F21164DSP@TSSOP20(UART ISP) [DX0001]
R5F21164DSP@TSSOP20(UART mode) [DX1000]
R5F21164SP@TSSOP20 [DX1000]
R5F21164SP@TSSOP20(single ISP) [DX0001]
R5F21164SP@TSSOP20(single wire) [DX1000]
R5F21164SP@TSSOP20(UART ISP) [DX0001]
R5F21164SP@TSSOP20(UART mode) [DX1000]

R5F21172DSP@TSSOP20 [DX1000]
R5F21172DSP@TSSOP20(single ISP) [DX0001]
R5F21172DSP@TSSOP20(single wire) [DX1000]
R5F21172DSP@TSSOP20(UART ISP) [DX0001]
R5F21172DSP@TSSOP20(UART mode) [DX1000]
R5F21172SP@TSSOP20 [DX1000]
R5F21172SP@TSSOP20(single ISP) [DX0001]
R5F21172SP@TSSOP20(single wire) [DX1000]
R5F21172SP@TSSOP20(UART ISP) [DX0001]
R5F21172SP@TSSOP20(UART mode) [DX1000]
R5F21173DSP@TSSOP20 [DX1000]
R5F21173DSP@TSSOP20(single ISP) [DX0001]
R5F21173DSP@TSSOP20(single wire) [DX1000]
R5F21173DSP@TSSOP20(UART ISP) [DX0001]
R5F21173DSP@TSSOP20(UART mode) [DX1000]
R5F21173SP@TSSOP20 [DX1000]
R5F21173SP@TSSOP20(single ISP) [DX0001]
R5F21173SP@TSSOP20(single wire) [DX1000]
R5F21173SP@TSSOP20(UART ISP) [DX0001]
R5F21173SP@TSSOP20(UART mode) [DX1000]
R5F21174DSP@TSSOP20 [DX1000]
R5F21174DSP@TSSOP20(single ISP) [DX0001]
R5F21174DSP@TSSOP20(single wire) [DX1000]
R5F21174DSP@TSSOP20(UART ISP) [DX0001]
R5F21174DSP@TSSOP20(UART mode) [DX1000]
R5F21174SP@TSSOP20 [DX1000]
R5F21174SP@TSSOP20(single ISP) [DX0001]
R5F21174SP@TSSOP20(single wire) [DX1000]
R5F21174SP@TSSOP20(UART ISP) [DX0001]
R5F21174SP@TSSOP20(UART mode) [DX1000]
R5F21181DD@SDIP20 [DX0032]
R5F21181DD@SDIP20(single ISP) [DX0001]
R5F21181DD@SDIP20(single wire) [DX0032]
R5F21181DD@SDIP20(UART ISP) [DX0001]
R5F21181DD@SDIP20(UART mode) [DX0032]
R5F21181DSP@TSSOP20 [DX1000]
R5F21181DSP@TSSOP20(single ISP) [DX0001]
R5F21181DSP@TSSOP20(single wire) [DX1000]
R5F21181DSP@TSSOP20(UART ISP) [DX0001]
R5F21181DSP@TSSOP20(UART mode) [DX1000]
R5F21181SP@TSSOP20 [DX1000]
R5F21181SP@TSSOP20(single ISP) [DX0001]
R5F21181SP@TSSOP20(single wire) [DX1000]
R5F21181SP@TSSOP20(UART ISP) [DX0001]
R5F21181SP@TSSOP20(UART mode) [DX1000]
R5F21182DD@SDIP20 [DX0032]
R5F21182DD@SDIP20(single ISP) [DX0001]
R5F21182DD@SDIP20(single wire) [DX0032]

R5F21182DD@SDIP20(UART ISP) [DX0001]
R5F21182DD@SDIP20(UART mode) [DX0032]
R5F21182DSP@TSSOP20 [DX1000]
R5F21182DSP@TSSOP20(single ISP) [DX0001]
R5F21182DSP@TSSOP20(single wire) [DX1000]
R5F21182DSP@TSSOP20(UART ISP) [DX0001]
R5F21182DSP@TSSOP20(UART mode) [DX1000]
R5F21182NP@QFN28 [DX4013]
R5F21182NP@QFN28(single ISP) [DX0001]
R5F21182NP@QFN28(single wire) [DX4013]
R5F21182NP@QFN28(UART ISP) [DX0001]
R5F21182NP@QFN28(UART mode) [DX4013]
R5F21182SP@TSSOP20 [DX1000]
R5F21182SP@TSSOP20(single ISP) [DX0001]
R5F21182SP@TSSOP20(single wire) [DX1000]
R5F21182SP@TSSOP20(UART ISP) [DX0001]
R5F21182SP@TSSOP20(UART mode) [DX1000]
R5F21183DD@SDIP20 [DX0032]
R5F21183DD@SDIP20(single ISP) [DX0001]
R5F21183DD@SDIP20(single wire) [DX0032]
R5F21183DD@SDIP20(UART ISP) [DX0001]
R5F21183DD@SDIP20(UART mode) [DX0032]
R5F21183DSP@TSSOP20 [DX1000]
R5F21183DSP@TSSOP20(single ISP) [DX0001]
R5F21183DSP@TSSOP20(single wire) [DX1000]
R5F21183DSP@TSSOP20(UART ISP) [DX0001]
R5F21183DSP@TSSOP20(UART mode) [DX1000]
R5F21183NP@QFN28 [DX4013]
R5F21183NP@QFN28(single ISP) [DX0001]
R5F21183NP@QFN28(single wire) [DX4013]
R5F21183NP@QFN28(UART ISP) [DX0001]
R5F21183NP@QFN28(UART mode) [DX4013]
R5F21183SP@TSSOP20 [DX1000]
R5F21183SP@TSSOP20(single ISP) [DX0001]
R5F21183SP@TSSOP20(single wire) [DX1000]
R5F21183SP@TSSOP20(UART ISP) [DX0001]
R5F21183SP@TSSOP20(UART mode) [DX1000]
R5F21184DD@SDIP20 [DX0032]
R5F21184DD@SDIP20(single ISP) [DX0001]
R5F21184DD@SDIP20(single wire) [DX0032]
R5F21184DD@SDIP20(UART ISP) [DX0001]
R5F21184DD@SDIP20(UART mode) [DX0032]
R5F21184DSP@TSSOP20 [DX1000]
R5F21184DSP@TSSOP20(single ISP) [DX0001]
R5F21184DSP@TSSOP20(single wire) [DX1000]
R5F21184DSP@TSSOP20(UART ISP) [DX0001]
R5F21184DSP@TSSOP20(UART mode) [DX1000]
R5F21184NP@QFN28 [DX4013]

R5F21184NP@QFN28(single ISP) [DX0001]
R5F21184NP@QFN28(single wire) [DX4013]
R5F21184NP@QFN28(UART ISP) [DX0001]
R5F21184NP@QFN28(UART mode) [DX4013]
R5F21184SP@TSSOP20 [DX1000]
R5F21184SP@TSSOP20(single ISP) [DX0001]
R5F21184SP@TSSOP20(single wire) [DX1000]
R5F21184SP@TSSOP20(UART ISP) [DX0001]
R5F21184SP@TSSOP20(UART mode) [DX1000]
R5F21191DD@SDIP20 [DX0032]
R5F21191DD@SDIP20(single ISP) [DX0001]
R5F21191DD@SDIP20(single wire) [DX0032]
R5F21191DD@SDIP20(UART ISP) [DX0001]
R5F21191DD@SDIP20(UART mode) [DX0032]
R5F21191DSP@TSSOP20 [DX1000]
R5F21191DSP@TSSOP20(single ISP) [DX0001]
R5F21191DSP@TSSOP20(single wire) [DX1000]
R5F21191DSP@TSSOP20(UART ISP) [DX0001]
R5F21191DSP@TSSOP20(UART mode) [DX1000]
R5F21191SP@TSSOP20 [DX1000]
R5F21191SP@TSSOP20(single ISP) [DX0001]
R5F21191SP@TSSOP20(single wire) [DX1000]
R5F21191SP@TSSOP20(UART ISP) [DX0001]
R5F21191SP@TSSOP20(UART mode) [DX1000]
R5F21192DD@SDIP20 [DX0032]
R5F21192DD@SDIP20(single ISP) [DX0001]
R5F21192DD@SDIP20(single wire) [DX0032]
R5F21192DD@SDIP20(UART ISP) [DX0001]
R5F21192DD@SDIP20(UART mode) [DX0032]
R5F21192DSP@TSSOP20 [DX1000]
R5F21192DSP@TSSOP20(single ISP) [DX0001]
R5F21192DSP@TSSOP20(single wire) [DX1000]
R5F21192DSP@TSSOP20(UART ISP) [DX0001]
R5F21192DSP@TSSOP20(UART mode) [DX1000]
R5F21192NP@QFN28 [DX4013]
R5F21192NP@QFN28(single ISP) [DX0001]
R5F21192NP@QFN28(single wire) [DX4013]
R5F21192NP@QFN28(UART ISP) [DX0001]
R5F21192NP@QFN28(UART mode) [DX4013]
R5F21192SP@TSSOP20 [DX1000]
R5F21192SP@TSSOP20(single ISP) [DX0001]
R5F21192SP@TSSOP20(single wire) [DX1000]
R5F21192SP@TSSOP20(UART ISP) [DX0001]
R5F21192SP@TSSOP20(UART mode) [DX1000]
R5F21193DD@SDIP20 [DX0032]
R5F21193DD@SDIP20(single ISP) [DX0001]
R5F21193DD@SDIP20(single wire) [DX0032]
R5F21193DD@SDIP20(UART ISP) [DX0001]

R5F21193DD@SDIP20(UART mode) [DX0032]
R5F21193DSP@TSSOP20 [DX1000]
R5F21193DSP@TSSOP20(single ISP) [DX0001]
R5F21193DSP@TSSOP20(single wire) [DX1000]
R5F21193DSP@TSSOP20(UART ISP) [DX0001]
R5F21193DSP@TSSOP20(UART mode) [DX1000]
R5F21193NP@QFN28 [DX4013]
R5F21193NP@QFN28(single ISP) [DX0001]
R5F21193NP@QFN28(single wire) [DX4013]
R5F21193NP@QFN28(UART ISP) [DX0001]
R5F21193NP@QFN28(UART mode) [DX4013]
R5F21193SP@TSSOP20 [DX1000]
R5F21193SP@TSSOP20(single ISP) [DX0001]
R5F21193SP@TSSOP20(single wire) [DX1000]
R5F21193SP@TSSOP20(UART ISP) [DX0001]
R5F21193SP@TSSOP20(UART mode) [DX1000]
R5F21194DD@SDIP20 [DX0032]
R5F21194DD@SDIP20(single ISP) [DX0001]
R5F21194DD@SDIP20(single wire) [DX0032]
R5F21194DD@SDIP20(UART ISP) [DX0001]
R5F21194DD@SDIP20(UART mode) [DX0032]
R5F21194DSP@TSSOP20 [DX1000]
R5F21194DSP@TSSOP20(single ISP) [DX0001]
R5F21194DSP@TSSOP20(single wire) [DX1000]
R5F21194DSP@TSSOP20(UART ISP) [DX0001]
R5F21194DSP@TSSOP20(UART mode) [DX1000]
R5F21194NP@QFN28 [DX4013]
R5F21194NP@QFN28(single ISP) [DX0001]
R5F21194NP@QFN28(single wire) [DX4013]
R5F21194NP@QFN28(UART ISP) [DX0001]
R5F21194NP@QFN28(UART mode) [DX4013]
R5F21194SP@TSSOP20 [DX1000]
R5F21194SP@TSSOP20(single ISP) [DX0001]
R5F21194SP@TSSOP20(single wire) [DX1000]
R5F21194SP@TSSOP20(UART ISP) [DX0001]
R5F21194SP@TSSOP20(UART mode) [DX1000]
R5F211A1DD@SDIP20 [DX0032]
R5F211A1DD@SDIP20(single ISP) [DX0001]
R5F211A1DD@SDIP20(single wire) [DX0032]
R5F211A1DD@SDIP20(UART ISP) [DX0001]
R5F211A1DD@SDIP20(UART mode) [DX0032]
R5F211A1DSP@TSSOP20 [DX1000]
R5F211A1DSP@TSSOP20(single ISP) [DX0001]
R5F211A1DSP@TSSOP20(single wire) [DX1000]
R5F211A1DSP@TSSOP20(UART ISP) [DX0001]
R5F211A1DSP@TSSOP20(UART mode) [DX1000]
R5F211A1SP@TSSOP20 [DX1000]
R5F211A1SP@TSSOP20(single ISP) [DX0001]

R5F211A1SP@TSSOP20(single wire) [DX1000]
R5F211A1SP@TSSOP20(UART ISP) [DX0001]
R5F211A1SP@TSSOP20(UART mode) [DX1000]
R5F211A2DD@SDIP20 [DX0032]
R5F211A2DD@SDIP20(single ISP) [DX0001]
R5F211A2DD@SDIP20(single wire) [DX0032]
R5F211A2DD@SDIP20(UART ISP) [DX0001]
R5F211A2DD@SDIP20(UART mode) [DX0032]
R5F211A2DSP@TSSOP20 [DX1000]
R5F211A2DSP@TSSOP20(single ISP) [DX0001]
R5F211A2DSP@TSSOP20(single wire) [DX1000]
R5F211A2DSP@TSSOP20(UART ISP) [DX0001]
R5F211A2DSP@TSSOP20(UART mode) [DX1000]
R5F211A2NP@QFN28 [DX4013]
R5F211A2NP@QFN28(single ISP) [DX0001]
R5F211A2NP@QFN28(single wire) [DX4013]
R5F211A2NP@QFN28(UART ISP) [DX0001]
R5F211A2NP@QFN28(UART mode) [DX4013]
R5F211A2SP@TSSOP20 [DX1000]
R5F211A2SP@TSSOP20(single ISP) [DX0001]
R5F211A2SP@TSSOP20(single wire) [DX1000]
R5F211A2SP@TSSOP20(UART ISP) [DX0001]
R5F211A2SP@TSSOP20(UART mode) [DX1000]
R5F211A3DD@SDIP20 [DX0032]
R5F211A3DD@SDIP20(single ISP) [DX0001]
R5F211A3DD@SDIP20(single wire) [DX0032]
R5F211A3DD@SDIP20(UART ISP) [DX0001]
R5F211A3DD@SDIP20(UART mode) [DX0032]
R5F211A3DSP@TSSOP20 [DX1000]
R5F211A3DSP@TSSOP20(single ISP) [DX0001]
R5F211A3DSP@TSSOP20(single wire) [DX1000]
R5F211A3DSP@TSSOP20(UART ISP) [DX0001]
R5F211A3DSP@TSSOP20(UART mode) [DX1000]
R5F211A3NP@QFN28 [DX4013]
R5F211A3NP@QFN28(single ISP) [DX0001]
R5F211A3NP@QFN28(single wire) [DX4013]
R5F211A3NP@QFN28(UART ISP) [DX0001]
R5F211A3NP@QFN28(UART mode) [DX4013]
R5F211A3SP@TSSOP20 [DX1000]
R5F211A3SP@TSSOP20(single ISP) [DX0001]
R5F211A3SP@TSSOP20(single wire) [DX1000]
R5F211A3SP@TSSOP20(UART ISP) [DX0001]
R5F211A3SP@TSSOP20(UART mode) [DX1000]
R5F211A4DD@SDIP20 [DX0032]
R5F211A4DD@SDIP20(single ISP) [DX0001]
R5F211A4DD@SDIP20(single wire) [DX0032]
R5F211A4DD@SDIP20(UART ISP) [DX0001]
R5F211A4DD@SDIP20(UART mode) [DX0032]

R5F211A4DSP@TSSOP20 [DX1000]
R5F211A4DSP@TSSOP20(single ISP) [DX0001]
R5F211A4DSP@TSSOP20(single wire) [DX1000]
R5F211A4DSP@TSSOP20(UART ISP) [DX0001]
R5F211A4DSP@TSSOP20(UART mode) [DX1000]
R5F211A4NP@QFN28 [DX4013]
R5F211A4NP@QFN28(single ISP) [DX0001]
R5F211A4NP@QFN28(single wire) [DX4013]
R5F211A4NP@QFN28(UART ISP) [DX0001]
R5F211A4NP@QFN28(UART mode) [DX4013]
R5F211A4SP@TSSOP20 [DX1000]
R5F211A4SP@TSSOP20(single ISP) [DX0001]
R5F211A4SP@TSSOP20(single wire) [DX1000]
R5F211A4SP@TSSOP20(UART ISP) [DX0001]
R5F211A4SP@TSSOP20(UART mode) [DX1000]
R5F211B1DD@SDIP20 [DX0032]
R5F211B1DD@SDIP20(single ISP) [DX0001]
R5F211B1DD@SDIP20(single wire) [DX0032]
R5F211B1DD@SDIP20(UART ISP) [DX0001]
R5F211B1DD@SDIP20(UART mode) [DX0032]
R5F211B1DSP@TSSOP20 [DX1000]
R5F211B1DSP@TSSOP20(single ISP) [DX0001]
R5F211B1DSP@TSSOP20(single wire) [DX1000]
R5F211B1DSP@TSSOP20(UART ISP) [DX0001]
R5F211B1DSP@TSSOP20(UART mode) [DX1000]
R5F211B1SP@TSSOP20 [DX1000]
R5F211B1SP@TSSOP20(single ISP) [DX0001]
R5F211B1SP@TSSOP20(single wire) [DX1000]
R5F211B1SP@TSSOP20(UART ISP) [DX0001]
R5F211B1SP@TSSOP20(UART mode) [DX1000]
R5F211B2DD@SDIP20 [DX0032]
R5F211B2DD@SDIP20(single ISP) [DX0001]
R5F211B2DD@SDIP20(single wire) [DX0032]
R5F211B2DD@SDIP20(UART ISP) [DX0001]
R5F211B2DD@SDIP20(UART mode) [DX0032]
R5F211B2DSP@TSSOP20 [DX1000]
R5F211B2DSP@TSSOP20(single ISP) [DX0001]
R5F211B2DSP@TSSOP20(single wire) [DX1000]
R5F211B2DSP@TSSOP20(UART ISP) [DX0001]
R5F211B2DSP@TSSOP20(UART mode) [DX1000]
R5F211B2NP@QFN28 [DX4013]
R5F211B2NP@QFN28(single ISP) [DX0001]
R5F211B2NP@QFN28(single wire) [DX4013]
R5F211B2NP@QFN28(UART ISP) [DX0001]
R5F211B2NP@QFN28(UART mode) [DX4013]
R5F211B2SP@TSSOP20 [DX1000]
R5F211B2SP@TSSOP20(single ISP) [DX0001]
R5F211B2SP@TSSOP20(single wire) [DX1000]

R5F211B2SP@TSSOP20(UART ISP) [DX0001]
R5F211B2SP@TSSOP20(UART mode) [DX1000]
R5F211B3DD@SDIP20 [DX0032]
R5F211B3DD@SDIP20(single ISP) [DX0001]
R5F211B3DD@SDIP20(single wire) [DX0032]
R5F211B3DD@SDIP20(UART ISP) [DX0001]
R5F211B3DD@SDIP20(UART mode) [DX0032]
R5F211B3DSP@TSSOP20 [DX1000]
R5F211B3DSP@TSSOP20(single ISP) [DX0001]
R5F211B3DSP@TSSOP20(single wire) [DX1000]
R5F211B3DSP@TSSOP20(UART ISP) [DX0001]
R5F211B3DSP@TSSOP20(UART mode) [DX1000]
R5F211B3NP@QFN28 [DX4013]
R5F211B3NP@QFN28(single ISP) [DX0001]
R5F211B3NP@QFN28(single wire) [DX4013]
R5F211B3NP@QFN28(UART ISP) [DX0001]
R5F211B3NP@QFN28(UART mode) [DX4013]
R5F211B3SP@TSSOP20 [DX1000]
R5F211B3SP@TSSOP20(single ISP) [DX0001]
R5F211B3SP@TSSOP20(single wire) [DX1000]
R5F211B3SP@TSSOP20(UART ISP) [DX0001]
R5F211B3SP@TSSOP20(UART mode) [DX1000]
R5F211B4DD@SDIP20 [DX0032]
R5F211B4DD@SDIP20(single ISP) [DX0001]
R5F211B4DD@SDIP20(single wire) [DX0032]
R5F211B4DD@SDIP20(UART ISP) [DX0001]
R5F211B4DD@SDIP20(UART mode) [DX0032]
R5F211B4DSP@TSSOP20 [DX1000]
R5F211B4DSP@TSSOP20(single ISP) [DX0001]
R5F211B4DSP@TSSOP20(single wire) [DX1000]
R5F211B4DSP@TSSOP20(UART ISP) [DX0001]
R5F211B4DSP@TSSOP20(UART mode) [DX1000]
R5F211B4NP@QFN28 [DX4013]
R5F211B4NP@QFN28(single ISP) [DX0001]
R5F211B4NP@QFN28(single wire) [DX4013]
R5F211B4NP@QFN28(UART ISP) [DX0001]
R5F211B4NP@QFN28(UART mode) [DX4013]
R5F211B4SP@TSSOP20 [DX1000]
R5F211B4SP@TSSOP20(single ISP) [DX0001]
R5F211B4SP@TSSOP20(single wire) [DX1000]
R5F211B4SP@TSSOP20(UART ISP) [DX0001]
R5F211B4SP@TSSOP20(UART mode) [DX1000]
R5F21206JFP@TQFP48 [DX3007]
R5F21206JFP@TQFP48(single ISP) [DX0001]
R5F21206JFP@TQFP48(single wire) [DX3007]
R5F21206KFP@TQFP48 [DX3007]
R5F21206KFP@TQFP48(single ISP) [DX0001]
R5F21206KFP@TQFP48(single wire) [DX3007]

R5F21207JFP@TQFP48 [DX3007]
R5F21207JFP@TQFP48(single ISP) [DX0001]
R5F21207JFP@TQFP48(single wire) [DX3007]
R5F21207KFP@TQFP48 [DX3007]
R5F21207KFP@TQFP48(single ISP) [DX0001]
R5F21207KFP@TQFP48(single wire) [DX3007]
R5F21208JFP@TQFP48 [DX3007]
R5F21208JFP@TQFP48(single ISP) [DX0001]
R5F21208JFP@TQFP48(single wire) [DX3007]
R5F21208KFP@TQFP48 [DX3007]
R5F21208KFP@TQFP48(single ISP) [DX0001]
R5F21208KFP@TQFP48(single wire) [DX3007]
R5F2120AJFP@TQFP48 [DX3007]
R5F2120AJFP@TQFP48(single ISP) [DX0001]
R5F2120AJFP@TQFP48(single wire) [DX3007]
R5F2120AKFP@TQFP48 [DX3007]
R5F2120AKFP@TQFP48(single ISP) [DX0001]
R5F2120AKFP@TQFP48(single wire) [DX3007]
R5F2120CJFP@TQFP48 [DX3007]
R5F2120CJFP@TQFP48(single ISP) [DX0001]
R5F2120CJFP@TQFP48(single wire) [DX3007]
R5F2120CKFP@TQFP48 [DX3007]
R5F2120CKFP@TQFP48(single ISP) [DX0001]
R5F2120CKFP@TQFP48(single wire) [DX3007]
R5F21216JFP@TQFP48 [DX3007]
R5F21216JFP@TQFP48(single ISP) [DX0001]
R5F21216JFP@TQFP48(single wire) [DX3007]
R5F21216KFP@TQFP48 [DX3007]
R5F21216KFP@TQFP48(single ISP) [DX0001]
R5F21216KFP@TQFP48(single wire) [DX3007]
R5F21217JFP@TQFP48 [DX3007]
R5F21217JFP@TQFP48(single ISP) [DX0001]
R5F21217JFP@TQFP48(single wire) [DX3007]
R5F21217KFP@TQFP48 [DX3007]
R5F21217KFP@TQFP48(single ISP) [DX0001]
R5F21217KFP@TQFP48(single wire) [DX3007]
R5F21218JFP@TQFP48 [DX3007]
R5F21218JFP@TQFP48(single ISP) [DX0001]
R5F21218JFP@TQFP48(single wire) [DX3007]
R5F21218KFP@TQFP48 [DX3007]
R5F21218KFP@TQFP48(single ISP) [DX0001]
R5F21218KFP@TQFP48(single wire) [DX3007]
R5F2121AJFP@TQFP48 [DX3007]
R5F2121AJFP@TQFP48(single ISP) [DX0001]
R5F2121AJFP@TQFP48(single wire) [DX3007]
R5F2121AKFP@TQFP48 [DX3007]
R5F2121AKFP@TQFP48(single ISP) [DX0001]
R5F2121AKFP@TQFP48(single wire) [DX3007]

R5F2121CJFP@TQFP48 [DX3007]
R5F2121CJFP@TQFP48(single ISP) [DX0001]
R5F2121CJFP@TQFP48(single wire) [DX3007]
R5F2121CKFP@TQFP48 [DX3007]
R5F2121CKFP@TQFP48(single ISP) [DX0001]
R5F2121CKFP@TQFP48(single wire) [DX3007]
R5F21226JFP@TQFP48 [DX3007]
R5F21226JFP@TQFP48(single ISP) [DX0001]
R5F21226JFP@TQFP48(single wire) [DX3007]
R5F21226KFP@TQFP48 [DX3007]
R5F21226KFP@TQFP48(single ISP) [DX0001]
R5F21226KFP@TQFP48(single wire) [DX3007]
R5F21227JFP@TQFP48 [DX3007]
R5F21227JFP@TQFP48(single ISP) [DX0001]
R5F21227JFP@TQFP48(single wire) [DX3007]
R5F21227KFP@TQFP48 [DX3007]
R5F21227KFP@TQFP48(single ISP) [DX0001]
R5F21227KFP@TQFP48(single wire) [DX3007]
R5F21228JFP@TQFP48 [DX3007]
R5F21228JFP@TQFP48(single ISP) [DX0001]
R5F21228JFP@TQFP48(single wire) [DX3007]
R5F21228KFP@TQFP48 [DX3007]
R5F21228KFP@TQFP48(single ISP) [DX0001]
R5F21228KFP@TQFP48(single wire) [DX3007]
R5F2122AJFP@TQFP48 [DX3007]
R5F2122AJFP@TQFP48(single ISP) [DX0001]
R5F2122AJFP@TQFP48(single wire) [DX3007]
R5F2122AKFP@TQFP48 [DX3007]
R5F2122AKFP@TQFP48(single ISP) [DX0001]
R5F2122AKFP@TQFP48(single wire) [DX3007]
R5F2122CJFP@TQFP48 [DX3007]
R5F2122CJFP@TQFP48(single ISP) [DX0001]
R5F2122CJFP@TQFP48(single wire) [DX3007]
R5F2122CKFP@TQFP48 [DX3007]
R5F2122CKFP@TQFP48(single ISP) [DX0001]
R5F2122CKFP@TQFP48(single wire) [DX3007]
R5F21236DFP@TQFP48 [DX3007]
R5F21236DFP@TQFP48(single wire) [DX3007]
R5F21236JFP@TQFP48 [DX3007]
R5F21236JFP@TQFP48(single ISP) [DX0001]
R5F21236JFP@TQFP48(single wire) [DX3007]
R5F21236KFP@TQFP48 [DX3007]
R5F21236KFP@TQFP48(single ISP) [DX0001]
R5F21236KFP@TQFP48(single wire) [DX3007]
R5F21237JFP@TQFP48 [DX3007]
R5F21237JFP@TQFP48(single ISP) [DX0001]
R5F21237JFP@TQFP48(single wire) [DX3007]
R5F21237KFP@TQFP48 [DX3007]

R5F21237KFP@TQFP48(single ISP) [DX0001]
R5F21237KFP@TQFP48(single wire) [DX3007]
R5F21238JFP@TQFP48 [DX3007]
R5F21238JFP@TQFP48(single ISP) [DX0001]
R5F21238JFP@TQFP48(single wire) [DX3007]
R5F21238KFP@TQFP48 [DX3007]
R5F21238KFP@TQFP48(single ISP) [DX0001]
R5F21238KFP@TQFP48(single wire) [DX3007]
R5F2123AJFP@TQFP48 [DX3007]
R5F2123AJFP@TQFP48(single ISP) [DX0001]
R5F2123AJFP@TQFP48(single wire) [DX3007]
R5F2123AKFP@TQFP48 [DX3007]
R5F2123AKFP@TQFP48(single ISP) [DX0001]
R5F2123AKFP@TQFP48(single wire) [DX3007]
R5F2123CJFP@TQFP48 [DX3007]
R5F2123CJFP@TQFP48(single ISP) [DX0001]
R5F2123CJFP@TQFP48(single wire) [DX3007]
R5F2123CKFP@TQFP48 [DX3007]
R5F2123CKFP@TQFP48(single ISP) [DX0001]
R5F2123CKFP@TQFP48(single wire) [DX3007]
R5F21244SDFP@TQFP52 [DX3010]
R5F21244SDFP@TQFP52(single ISP) [DX0001]
R5F21244SDFP@TQFP52(single wire) [DX3010]
R5F21244SDFP@TQFP52(UART ISP) [DX0001]
R5F21244SDFP@TQFP52(UART mode) [DX3010]
R5F21244SNFP@TQFP52 [DX3010]
R5F21244SNFP@TQFP52(single ISP) [DX0001]
R5F21244SNFP@TQFP52(single wire) [DX3010]
R5F21244SNFP@TQFP52(UART ISP) [DX0001]
R5F21244SNFP@TQFP52(UART mode) [DX3010]
R5F21245SDFP@TQFP52 [DX3010]
R5F21245SDFP@TQFP52(single wire) [DX3010]
R5F21245SDFP@TQFP52(UART ISP) [DX0001]
R5F21245SDFP@TQFP52(UART mode) [DX3010]
R5F21245SNFP@TQFP52 [DX3010]
R5F21245SNFP@TQFP52(single wire) [DX3010]
R5F21245SNFP@TQFP52(UART ISP) [DX0001]
R5F21245SNFP@TQFP52(UART mode) [DX3010]
R5F21246SDFP@TQFP52 [DX3010]
R5F21246SDFP@TQFP52(single ISP) [DX0001]
R5F21246SDFP@TQFP52(single wire) [DX3010]
R5F21246SDFP@TQFP52(UART ISP) [DX0001]
R5F21246SDFP@TQFP52(UART mode) [DX3010]
R5F21246SNFP@TQFP52 [DX3010]
R5F21246SNFP@TQFP52(single ISP) [DX0001]
R5F21246SNFP@TQFP52(single wire) [DX3010]
R5F21246SNFP@TQFP52(UART ISP) [DX0001]
R5F21246SNFP@TQFP52(UART mode) [DX3010]

R5F21247SDFP@TQFP52 [DX3010]
R5F21247SDFP@TQFP52(single ISP) [DX0001]
R5F21247SDFP@TQFP52(single wire) [DX3010]
R5F21247SDFP@TQFP52(UART ISP) [DX0001]
R5F21247SDFP@TQFP52(UART mode) [DX3010]
R5F21247SNFP@TQFP52 [DX3010]
R5F21247SNFP@TQFP52(single ISP) [DX0001]
R5F21247SNFP@TQFP52(single wire) [DX3010]
R5F21247SNFP@TQFP52(UART ISP) [DX0001]
R5F21247SNFP@TQFP52(UART mode) [DX3010]
R5F21248SDFP@TQFP52 [DX3010]
R5F21248SDFP@TQFP52(single ISP) [DX0001]
R5F21248SDFP@TQFP52(single wire) [DX3010]
R5F21248SDFP@TQFP52(UART ISP) [DX0001]
R5F21248SDFP@TQFP52(UART mode) [DX3010]
R5F21248SNFP@TQFP52 [DX3010]
R5F21248SNFP@TQFP52(single ISP) [DX0001]
R5F21248SNFP@TQFP52(single wire) [DX3010]
R5F21248SNFP@TQFP52(UART ISP) [DX0001]
R5F21248SNFP@TQFP52(UART mode) [DX3010]
R5F21254SDFP@TQFP52 [DX3010]
R5F21254SDFP@TQFP52(single ISP) [DX0001]
R5F21254SDFP@TQFP52(single wire) [DX3010]
R5F21254SDFP@TQFP52(UART ISP) [DX0001]
R5F21254SDFP@TQFP52(UART mode) [DX3010]
R5F21254SNFP@TQFP52 [DX3010]
R5F21254SNFP@TQFP52(single ISP) [DX0001]
R5F21254SNFP@TQFP52(single wire) [DX3010]
R5F21254SNFP@TQFP52(UART ISP) [DX0001]
R5F21254SNFP@TQFP52(UART mode) [DX3010]
R5F21254SYFP@TQFP52 [DX3010]　　R5F21255SDFP@TQFP52 [DX3010]
R5F21255SDFP@TQFP52(single wire) [DX3010]
R5F21255SDFP@TQFP52(UART mode) [DX3010]
R5F21255SNFP@TQFP52 [DX3010]
R5F21255SNFP@TQFP52(single wire) [DX3010]
R5F21255SNFP@TQFP52(UART mode) [DX3010]
R5F21255SYFP@TQFP52 [DX3010]　　R5F21256SDFP@TQFP52 [DX3010]
R5F21256SDFP@TQFP52(single ISP) [DX0001]
R5F21256SDFP@TQFP52(single wire) [DX3010]
R5F21256SDFP@TQFP52(UART ISP) [DX0001]
R5F21256SDFP@TQFP52(UART mode) [DX3010]
R5F21256SNFP@TQFP52 [DX3010]
R5F21256SNFP@TQFP52(single ISP) [DX0001]
R5F21256SNFP@TQFP52(single wire) [DX3010]
R5F21256SNFP@TQFP52(UART ISP) [DX0001]
R5F21256SNFP@TQFP52(UART mode) [DX3010]
R5F21256SYFP@TQFP52 [DX3010]　　R5F21257SDFP@TQFP52 [DX3010]
R5F21257SDFP@TQFP52(single ISP) [DX0001]

R5F21257SDFP@TQFP52(single wire) [DX3010]
R5F21257SDFP@TQFP52(UART ISP) [DX0001]
R5F21257SDFP@TQFP52(UART mode) [DX3010]
R5F21257SNFP@TQFP52 [DX3010]
R5F21257SNFP@TQFP52(single ISP) [DX0001]
R5F21257SNFP@TQFP52(single wire) [DX3010]
R5F21257SNFP@TQFP52(UART ISP) [DX0001]
R5F21257SNFP@TQFP52(UART mode) [DX3010]
R5F21257SYFP@TQFP52 [DX3010]
R5F21258SDFP@TQFP52 [DX3010]
R5F21258SDFP@TQFP52(single ISP) [DX0001]
R5F21258SDFP@TQFP52(single wire) [DX3010]
R5F21258SDFP@TQFP52(UART ISP) [DX0001]
R5F21258SDFP@TQFP52(UART mode) [DX3010]
R5F21258SNFP@TQFP52 [DX3010]
R5F21258SNFP@TQFP52(single ISP) [DX0001]
R5F21258SNFP@TQFP52(single wire) [DX3010]
R5F21258SNFP@TQFP52(UART ISP) [DX0001]
R5F21258SNFP@TQFP52(UART mode) [DX3010]
R5F21258SYFP@TQFP52 [DX3010]
R5F21262DFP@QFP32 [DX3061]
R5F21262DFP@QFP32(single ISP) [DX0001]
R5F21262DFP@QFP32(single wire) [DX3061]
R5F21262DFP@QFP32(UART ISP) [DX0001]
R5F21262DFP@QFP32(UART mode) [DX3061]
R5F21262JFP@QFP32 [DX3061]
R5F21262JFP@QFP32(single ISP) [DX0001]
R5F21262JFP@QFP32(single wire) [DX3061]
R5F21262JFP@QFP32(UART ISP) [DX0001]
R5F21262JFP@QFP32(UART mode) [DX3061]
R5F21262KFP@QFP32 [DX3061]
R5F21262KFP@QFP32(single ISP) [DX0001]
R5F21262KFP@QFP32(single wire) [DX3061]
R5F21262KFP@QFP32(UART ISP) [DX0001]
R5F21262KFP@QFP32(UART mode) [DX3061]
R5F21262NFP@QFP32 [DX3061]
R5F21262NFP@QFP32(single ISP) [DX0001]
R5F21262NFP@QFP32(single wire) [DX3061]
R5F21262NFP@QFP32(UART ISP) [DX0001]
R5F21262NFP@QFP32(UART mode) [DX3061]
R5F21262SDFP@QFP32 [DX3061]
R5F21262SDFP@QFP32(single ISP) [DX0001]
R5F21262SDFP@QFP32(single wire) [DX3061]
R5F21262SDFP@QFP32(UART ISP) [DX0001]
R5F21262SDFP@QFP32(UART mode) [DX3061]
R5F21262SJFP@QFP32 [DX3061]
R5F21262SJFP@QFP32(single ISP) [DX0001]
R5F21262SJFP@QFP32(single wire) [DX3061]
R5F21262SJFP@QFP32(UART ISP) [DX0001]
R5F21262SJFP@QFP32(UART mode) [DX3061]

R5F21262SKFP@QFP32 [DX3061]
R5F21262SKFP@QFP32(single ISP) [DX0001]
R5F21262SKFP@QFP32(single wire) [DX3061]
R5F21262SKFP@QFP32(UART ISP) [DX0001]
R5F21262SKFP@QFP32(UART mode) [DX3061]
R5F21262SNFP@QFP32 [DX3061]
R5F21262SNFP@QFP32(single ISP) [DX0001]
R5F21262SNFP@QFP32(single wire) [DX3061]
R5F21262SNFP@QFP32(UART ISP) [DX0001]
R5F21262SNFP@QFP32(UART mode) [DX3061]
R5F21264DFP@QFP32 [DX3061]
R5F21264DFP@QFP32(single ISP) [DX0001]
R5F21264DFP@QFP32(single wire) [DX3061]
R5F21264DFP@QFP32(UART ISP) [DX0001]
R5F21264DFP@QFP32(UART mode) [DX3061]
R5F21264JFP@QFP32 [DX3061]
R5F21264JFP@QFP32(single ISP) [DX0001]
R5F21264JFP@QFP32(single wire) [DX3061]
R5F21264JFP@QFP32(UART ISP) [DX0001]
R5F21264JFP@QFP32(UART mode) [DX3061]
R5F21264KFP@QFP32 [DX3061]
R5F21264KFP@QFP32(single ISP) [DX0001]
R5F21264KFP@QFP32(single wire) [DX3061]
R5F21264KFP@QFP32(UART ISP) [DX0001]
R5F21264KFP@QFP32(UART mode) [DX3061]
R5F21264NFP@QFP32 [DX3061]
R5F21264NFP@QFP32(single ISP) [DX0001]
R5F21264NFP@QFP32(single wire) [DX3061]
R5F21264NFP@QFP32(UART ISP) [DX0001]
R5F21264NFP@QFP32(UART mode) [DX3061]
R5F21264SDFP@QFP32 [DX3061]
R5F21264SDFP@QFP32(single ISP) [DX0001]
R5F21264SDFP@QFP32(single wire) [DX3061]
R5F21264SDFP@QFP32(UART ISP) [DX0001]
R5F21264SDFP@QFP32(UART mode) [DX3061]
R5F21264SJFP@QFP32 [DX3061]
R5F21264SJFP@QFP32(single ISP) [DX0001]
R5F21264SJFP@QFP32(single wire) [DX3061]
R5F21264SJFP@QFP32(UART ISP) [DX0001]
R5F21264SJFP@QFP32(UART mode) [DX3061]
R5F21264SKFP@QFP32 [DX3061]
R5F21264SKFP@QFP32(single ISP) [DX0001]
R5F21264SKFP@QFP32(single wire) [DX3061]
R5F21264SKFP@QFP32(UART ISP) [DX0001]
R5F21264SKFP@QFP32(UART mode) [DX3061]
R5F21264SNFP@QFP32 [DX3061]
R5F21264SNFP@QFP32(single ISP) [DX0001]
R5F21264SNFP@QFP32(single wire) [DX3061]

R5F21264SNFP@QFP32(UART ISP) [DX0001]
R5F21264SNFP@QFP32(UART mode) [DX3061]
R5F21265DFP@QFP32 [DX3061]
R5F21265DFP@QFP32(single ISP) [DX0001]
R5F21265DFP@QFP32(single wire) [DX3061]
R5F21265DFP@QFP32(UART ISP) [DX0001]
R5F21265DFP@QFP32(UART mode) [DX3061]
R5F21265JFP@QFP32 [DX3061]
R5F21265JFP@QFP32(single ISP) [DX0001]
R5F21265JFP@QFP32(single wire) [DX3061]
R5F21265JFP@QFP32(UART ISP) [DX0001]
R5F21265JFP@QFP32(UART mode) [DX3061]
R5F21265KFP@QFP32 [DX3061]
R5F21265KFP@QFP32(single ISP) [DX0001]
R5F21265KFP@QFP32(single wire) [DX3061]
R5F21265KFP@QFP32(UART ISP) [DX0001]
R5F21265KFP@QFP32(UART mode) [DX3061]
R5F21265NFP@QFP32 [DX3061]
R5F21265NFP@QFP32(single ISP) [DX0001]
R5F21265NFP@QFP32(single wire) [DX3061]
R5F21265NFP@QFP32(UART ISP) [DX0001]
R5F21265NFP@QFP32(UART mode) [DX3061]
R5F21265SDFP@QFP32 [DX3061]
R5F21265SDFP@QFP32(single ISP) [DX0001]
R5F21265SDFP@QFP32(single wire) [DX3061]
R5F21265SDFP@QFP32(UART ISP) [DX0001]
R5F21265SDFP@QFP32(UART mode) [DX3061]
R5F21265SJFP@QFP32 [DX3061]
R5F21265SJFP@QFP32(single ISP) [DX0001]
R5F21265SJFP@QFP32(single wire) [DX3061]
R5F21265SJFP@QFP32(UART ISP) [DX0001]
R5F21265SJFP@QFP32(UART mode) [DX3061]
R5F21265SKFP@QFP32 [DX3061]
R5F21265SKFP@QFP32(single ISP) [DX0001]
R5F21265SKFP@QFP32(single wire) [DX3061]
R5F21265SKFP@QFP32(UART ISP) [DX0001]
R5F21265SKFP@QFP32(UART mode) [DX3061]
R5F21265SNFP@QFP32 [DX3061]
R5F21265SNFP@QFP32(single ISP) [DX0001]
R5F21265SNFP@QFP32(single wire) [DX3061]
R5F21265SNFP@QFP32(UART ISP) [DX0001]
R5F21265SNFP@QFP32(UART mode) [DX3061]
R5F21266DFP@QFP32 [DX3061]
R5F21266DFP@QFP32(single ISP) [DX0001]
R5F21266DFP@QFP32(single wire) [DX3061]
R5F21266DFP@QFP32(UART ISP) [DX0001]
R5F21266DFP@QFP32(UART mode) [DX3061]
R5F21266JFP@QFP32 [DX3061]

R5F21266JFP@QFP32(single ISP) [DX0001]
R5F21266JFP@QFP32(single wire) [DX3061]
R5F21266JFP@QFP32(UART ISP) [DX0001]
R5F21266JFP@QFP32(UART mode) [DX3061]
R5F21266KFP@QFP32 [DX3061]
R5F21266KFP@QFP32(single ISP) [DX0001]
R5F21266KFP@QFP32(single wire) [DX3061]
R5F21266KFP@QFP32(UART ISP) [DX0001]
R5F21266KFP@QFP32(UART mode) [DX3061]
R5F21266NFP@QFP32 [DX3061]
R5F21266NFP@QFP32(single ISP) [DX0001]
R5F21266NFP@QFP32(single wire) [DX3061]
R5F21266NFP@QFP32(UART ISP) [DX0001]
R5F21266NFP@QFP32(UART mode) [DX3061]
R5F21266SDFP@QFP32 [DX3061]
R5F21266SDFP@QFP32(single ISP) [DX0001]
R5F21266SDFP@QFP32(single wire) [DX3061]
R5F21266SDFP@QFP32(UART ISP) [DX0001]
R5F21266SDFP@QFP32(UART mode) [DX3061]
R5F21266SJFP@QFP32 [DX3061]
R5F21266SJFP@QFP32(single ISP) [DX0001]
R5F21266SJFP@QFP32(single wire) [DX3061]
R5F21266SJFP@QFP32(UART ISP) [DX0001]
R5F21266SJFP@QFP32(UART mode) [DX3061]
R5F21266SKFP@QFP32 [DX3061]
R5F21266SKFP@QFP32(single ISP) [DX0001]
R5F21266SKFP@QFP32(single wire) [DX3061]
R5F21266SKFP@QFP32(UART ISP) [DX0001]
R5F21266SKFP@QFP32(UART mode) [DX3061]
R5F21266SNFP@QFP32 [DX3061]
R5F21266SNFP@QFP32(single ISP) [DX0001]
R5F21266SNFP@QFP32(single wire) [DX3061]
R5F21266SNFP@QFP32(UART ISP) [DX0001]
R5F21266SNFP@QFP32(UART mode) [DX3061]
R5F21272DFP@QFP32 [DX3061]
R5F21272DFP@QFP32(single ISP) [DX0001]
R5F21272DFP@QFP32(single wire) [DX3061]
R5F21272DFP@QFP32(UART ISP) [DX0001]
R5F21272DFP@QFP32(UART mode) [DX3061]
R5F21272JFP@QFP32 [DX3061]
R5F21272JFP@QFP32(single ISP) [DX0001]
R5F21272JFP@QFP32(single wire) [DX3061]
R5F21272JFP@QFP32(UART ISP) [DX0001]
R5F21272JFP@QFP32(UART mode) [DX3061]
R5F21272KFP@QFP32 [DX3061]
R5F21272KFP@QFP32(single ISP) [DX0001]
R5F21272KFP@QFP32(single wire) [DX3061]
R5F21272KFP@QFP32(UART ISP) [DX0001]

R5F21272KFP@QFP32(UART mode) [DX3061]
R5F21272NFP@QFP32 [DX3061]
R5F21272NFP@QFP32(single ISP) [DX0001]
R5F21272NFP@QFP32(single wire) [DX3061]
R5F21272NFP@QFP32(UART ISP) [DX0001]
R5F21272NFP@QFP32(UART mode) [DX3061]
R5F21272SDFP@QFP32 [DX3061]
R5F21272SDFP@QFP32(single ISP) [DX0001]
R5F21272SDFP@QFP32(single wire) [DX3061]
R5F21272SDFP@QFP32(UART ISP) [DX0001]
R5F21272SDFP@QFP32(UART mode) [DX3061]
R5F21272SJFP@QFP32 [DX3061]
R5F21272SJFP@QFP32(single ISP) [DX0001]
R5F21272SJFP@QFP32(single wire) [DX3061]
R5F21272SJFP@QFP32(UART ISP) [DX0001]
R5F21272SJFP@QFP32(UART mode) [DX3061]
R5F21272SKFP@QFP32 [DX3061]
R5F21272SKFP@QFP32(single ISP) [DX0001]
R5F21272SKFP@QFP32(single wire) [DX3061]
R5F21272SKFP@QFP32(UART ISP) [DX0001]
R5F21272SKFP@QFP32(UART mode) [DX3061]
R5F21272SNFP@QFP32 [DX3061]
R5F21272SNFP@QFP32(single ISP) [DX0001]
R5F21272SNFP@QFP32(single wire) [DX3061]
R5F21272SNFP@QFP32(UART ISP) [DX0001]
R5F21272SNFP@QFP32(UART mode) [DX3061]
R5F21274DFP@QFP32 [DX3061]
R5F21274DFP@QFP32(single ISP) [DX0001]
R5F21274DFP@QFP32(single wire) [DX3061]
R5F21274DFP@QFP32(UART ISP) [DX0001]
R5F21274DFP@QFP32(UART mode) [DX3061]
R5F21274JFP@QFP32 [DX3061]
R5F21274JFP@QFP32(single ISP) [DX0001]
R5F21274JFP@QFP32(single wire) [DX3061]
R5F21274JFP@QFP32(UART ISP) [DX0001]
R5F21274JFP@QFP32(UART mode) [DX3061]
R5F21274KFP@QFP32 [DX3061]
R5F21274KFP@QFP32(single ISP) [DX0001]
R5F21274KFP@QFP32(single wire) [DX3061]
R5F21274KFP@QFP32(UART ISP) [DX0001]
R5F21274KFP@QFP32(UART mode) [DX3061]
R5F21274NFP@QFP32 [DX3061]
R5F21274NFP@QFP32(single ISP) [DX0001]
R5F21274NFP@QFP32(single wire) [DX3061]
R5F21274NFP@QFP32(UART ISP) [DX0001]
R5F21274NFP@QFP32(UART mode) [DX3061]
R5F21274SDFP@QFP32 [DX3061]
R5F21274SDFP@QFP32(single ISP) [DX0001]

R5F21274SDFP@QFP32(single wire) [DX3061]
R5F21274SDFP@QFP32(UART ISP) [DX0001]
R5F21274SDFP@QFP32(UART mode) [DX3061]
R5F21274SJFP@QFP32 [DX3061]
R5F21274SJFP@QFP32(single ISP) [DX0001]
R5F21274SJFP@QFP32(single wire) [DX3061]
R5F21274SJFP@QFP32(UART ISP) [DX0001]
R5F21274SJFP@QFP32(UART mode) [DX3061]
R5F21274SKFP@QFP32 [DX3061]
R5F21274SKFP@QFP32(single ISP) [DX0001]
R5F21274SKFP@QFP32(single wire) [DX3061]
R5F21274SKFP@QFP32(UART ISP) [DX0001]
R5F21274SKFP@QFP32(UART mode) [DX3061]
R5F21274SNFP@QFP32 [DX3061]
R5F21274SNFP@QFP32(single ISP) [DX0001]
R5F21274SNFP@QFP32(single wire) [DX3061]
R5F21274SNFP@QFP32(UART ISP) [DX0001]
R5F21274SNFP@QFP32(UART mode) [DX3061]
R5F21275DFP@QFP32 [DX3061]
R5F21275DFP@QFP32(single ISP) [DX0001]
R5F21275DFP@QFP32(single wire) [DX3061]
R5F21275DFP@QFP32(UART ISP) [DX0001]
R5F21275DFP@QFP32(UART mode) [DX3061]
R5F21275JFP@QFP32 [DX3061]
R5F21275JFP@QFP32(single ISP) [DX0001]
R5F21275JFP@QFP32(single wire) [DX3061]
R5F21275JFP@QFP32(UART ISP) [DX0001]
R5F21275JFP@QFP32(UART mode) [DX3061]
R5F21275KFP@QFP32 [DX3061]
R5F21275KFP@QFP32(single ISP) [DX0001]
R5F21275KFP@QFP32(single wire) [DX3061]
R5F21275KFP@QFP32(UART ISP) [DX0001]
R5F21275KFP@QFP32(UART mode) [DX3061]
R5F21275NFP@QFP32 [DX3061]
R5F21275NFP@QFP32(single ISP) [DX0001]
R5F21275NFP@QFP32(single wire) [DX3061]
R5F21275NFP@QFP32(UART ISP) [DX0001]
R5F21275NFP@QFP32(UART mode) [DX3061]
R5F21275SDFP@QFP32 [DX3061]
R5F21275SDFP@QFP32(single ISP) [DX0001]
R5F21275SDFP@QFP32(single wire) [DX3061]
R5F21275SDFP@QFP32(UART ISP) [DX0001]
R5F21275SDFP@QFP32(UART mode) [DX3061]
R5F21275SJFP@QFP32 [DX3061]
R5F21275SJFP@QFP32(single ISP) [DX0001]
R5F21275SJFP@QFP32(single wire) [DX3061]
R5F21275SJFP@QFP32(UART ISP) [DX0001]
R5F21275SJFP@QFP32(UART mode) [DX3061]

R5F21275SKFP@QFP32 [DX3061]
R5F21275SKFP@QFP32(single ISP) [DX0001]
R5F21275SKFP@QFP32(single wire) [DX3061]
R5F21275SKFP@QFP32(UART ISP) [DX0001]
R5F21275SKFP@QFP32(UART mode) [DX3061]
R5F21275SNFP@QFP32 [DX3061]
R5F21275SNFP@QFP32(single ISP) [DX0001]
R5F21275SNFP@QFP32(single wire) [DX3061]
R5F21275SNFP@QFP32(UART ISP) [DX0001]
R5F21275SNFP@QFP32(UART mode) [DX3061]
R5F21276DFP@QFP32 [DX3061]
R5F21276DFP@QFP32(single ISP) [DX0001]
R5F21276DFP@QFP32(single wire) [DX3061]
R5F21276DFP@QFP32(UART ISP) [DX0001]
R5F21276DFP@QFP32(UART mode) [DX3061]
R5F21276JFP@QFP32 [DX3061]
R5F21276JFP@QFP32(single ISP) [DX0001]
R5F21276JFP@QFP32(single wire) [DX3061]
R5F21276JFP@QFP32(UART ISP) [DX0001]
R5F21276JFP@QFP32(UART mode) [DX3061]
R5F21276KFP@QFP32 [DX3061]
R5F21276KFP@QFP32(single ISP) [DX0001]
R5F21276KFP@QFP32(single wire) [DX3061]
R5F21276KFP@QFP32(UART ISP) [DX0001]
R5F21276KFP@QFP32(UART mode) [DX3061]
R5F21276NFP@QFP32 [DX3061]
R5F21276NFP@QFP32(single ISP) [DX0001]
R5F21276NFP@QFP32(single wire) [DX3061]
R5F21276NFP@QFP32(UART ISP) [DX0001]
R5F21276NFP@QFP32(UART mode) [DX3061]
R5F21276SDFP@QFP32 [DX3061]
R5F21276SDFP@QFP32(single ISP) [DX0001]
R5F21276SDFP@QFP32(single wire) [DX3061]
R5F21276SDFP@QFP32(UART ISP) [DX0001]
R5F21276SDFP@QFP32(UART mode) [DX3061]
R5F21276SJFP@QFP32 [DX3061]
R5F21276SJFP@QFP32(single ISP) [DX0001]
R5F21276SJFP@QFP32(single wire) [DX3061]
R5F21276SJFP@QFP32(UART ISP) [DX0001]
R5F21276SJFP@QFP32(UART mode) [DX3061]
R5F21276SKFP@QFP32 [DX3061]
R5F21276SKFP@QFP32(single ISP) [DX0001]
R5F21276SKFP@QFP32(single wire) [DX3061]
R5F21276SKFP@QFP32(UART ISP) [DX0001]
R5F21276SKFP@QFP32(UART mode) [DX3061]
R5F21276SNFP@QFP32 [DX3061]
R5F21276SNFP@QFP32(single ISP) [DX0001]
R5F21276SNFP@QFP32(single wire) [DX3061]

R5F21276SNFP@QFP32(UART ISP) [DX0001]
R5F21276SNFP@QFP32(UART mode) [DX3061]
R5F21282DSP@SOIC20 [DX1000]
R5F21282DSP@SOIC20(single ISP) [DX0001]
R5F21282DSP@SOIC20(single wire) [DX1000]
R5F21282DSP@SOIC20(UART ISP) [DX0001]
R5F21282DSP@SOIC20(UART mode) [DX1000]
R5F21282JSP@SOIC20 [DX1000]
R5F21282JSP@SOIC20(single ISP) [DX0001]
R5F21282JSP@SOIC20(single wire) [DX1000]
R5F21282JSP@SOIC20(UART ISP) [DX0001]
R5F21282JSP@SOIC20(UART mode) [DX1000]
R5F21282KSP@SOIC20 [DX1000]
R5F21282KSP@SOIC20(single ISP) [DX0001]
R5F21282KSP@SOIC20(single wire) [DX1000]
R5F21282KSP@SOIC20(UART ISP) [DX0001]
R5F21282KSP@SOIC20(UART mode) [DX1000]
R5F21282NSP@SOIC20 [DX1000]
R5F21282NSP@SOIC20(single ISP) [DX0001]
R5F21282NSP@SOIC20(single wire) [DX1000]
R5F21282NSP@SOIC20(UART ISP) [DX0001]
R5F21282NSP@SOIC20(UART mode) [DX1000]
R5F21282SDSP@SOIC20 [DX1000]
R5F21282SDSP@SOIC20(single ISP) [DX0001]
R5F21282SDSP@SOIC20(single wire) [DX1000]
R5F21282SDSP@SOIC20(UART ISP) [DX0001]
R5F21282SDSP@SOIC20(UART mode) [DX1000]
R5F21282SJSP@SOIC20 [DX1000]
R5F21282SJSP@SOIC20(single ISP) [DX0001]
R5F21282SJSP@SOIC20(single wire) [DX1000]
R5F21282SJSP@SOIC20(UART ISP) [DX0001]
R5F21282SJSP@SOIC20(UART mode) [DX1000]
R5F21282SKSP@SOIC20 [DX1000]
R5F21282SKSP@SOIC20(single ISP) [DX0001]
R5F21282SKSP@SOIC20(single wire) [DX1000]
R5F21282SKSP@SOIC20(UART ISP) [DX0001]
R5F21282SKSP@SOIC20(UART mode) [DX1000]
R5F21282SNSP@SOIC20 [DX1000]
R5F21282SNSP@SOIC20(single ISP) [DX0001]
R5F21282SNSP@SOIC20(single wire) [DX1000]
R5F21282SNSP@SOIC20(UART ISP) [DX0001]
R5F21282SNSP@SOIC20(UART mode) [DX1000]
R5F21284DSP@SOIC20 [DX1000]
R5F21284DSP@SOIC20(single ISP) [DX0001]
R5F21284DSP@SOIC20(single wire) [DX1000]
R5F21284DSP@SOIC20(UART ISP) [DX0001]
R5F21284DSP@SOIC20(UART mode) [DX1000]
R5F21284JSP@SOIC20 [DX1000]

R5F21284JSP@SOIC20(single ISP) [DX0001]
R5F21284JSP@SOIC20(single wire) [DX1000]
R5F21284JSP@SOIC20(UART ISP) [DX0001]
R5F21284JSP@SOIC20(UART mode) [DX1000]
R5F21284KSP@SOIC20 [DX1000]
R5F21284KSP@SOIC20(single ISP) [DX0001]
R5F21284KSP@SOIC20(single wire) [DX1000]
R5F21284KSP@SOIC20(UART ISP) [DX0001]
R5F21284KSP@SOIC20(UART mode) [DX1000]
R5F21284NSP@SOIC20 [DX1000]
R5F21284NSP@SOIC20(single ISP) [DX0001]
R5F21284NSP@SOIC20(single wire) [DX1000]
R5F21284NSP@SOIC20(UART ISP) [DX0001]
R5F21284NSP@SOIC20(UART mode) [DX1000]
R5F21284SDSP@SOIC20 [DX1000]
R5F21284SDSP@SOIC20(single ISP) [DX0001]
R5F21284SDSP@SOIC20(single wire) [DX1000]
R5F21284SDSP@SOIC20(UART ISP) [DX0001]
R5F21284SDSP@SOIC20(UART mode) [DX1000]
R5F21284SJSP@SOIC20 [DX1000]
R5F21284SJSP@SOIC20(single ISP) [DX0001]
R5F21284SJSP@SOIC20(single wire) [DX1000]
R5F21284SJSP@SOIC20(UART ISP) [DX0001]
R5F21284SJSP@SOIC20(UART mode) [DX1000]
R5F21284SKSP@SOIC20 [DX1000]
R5F21284SKSP@SOIC20(single ISP) [DX0001]
R5F21284SKSP@SOIC20(single wire) [DX1000]
R5F21284SKSP@SOIC20(UART ISP) [DX0001]
R5F21284SKSP@SOIC20(UART mode) [DX1000]
R5F21284SNSP@SOIC20 [DX1000]
R5F21284SNSP@SOIC20(single ISP) [DX0001]
R5F21284SNSP@SOIC20(single wire) [DX1000]
R5F21284SNSP@SOIC20(UART ISP) [DX0001]
R5F21284SNSP@SOIC20(UART mode) [DX1000]
R5F21292DSP@SOIC20 [DX1000]
R5F21292DSP@SOIC20(single ISP) [DX0001]
R5F21292DSP@SOIC20(single wire) [DX1000]
R5F21292DSP@SOIC20(UART ISP) [DX0001]
R5F21292DSP@SOIC20(UART mode) [DX1000]
R5F21292JSP@SOIC20 [DX1000]
R5F21292JSP@SOIC20(single ISP) [DX0001]
R5F21292JSP@SOIC20(single wire) [DX1000]
R5F21292JSP@SOIC20(UART ISP) [DX0001]
R5F21292JSP@SOIC20(UART mode) [DX1000]
R5F21292KSP@SOIC20 [DX1000]
R5F21292KSP@SOIC20(single ISP) [DX0001]
R5F21292KSP@SOIC20(single wire) [DX1000]
R5F21292KSP@SOIC20(UART ISP) [DX0001]

R5F21292KSP@SOIC20(UART mode) [DX1000]
R5F21292NSP@SOIC20 [DX1000]
R5F21292NSP@SOIC20(single ISP) [DX0001]
R5F21292NSP@SOIC20(single wire) [DX1000]
R5F21292NSP@SOIC20(UART ISP) [DX0001]
R5F21292NSP@SOIC20(UART mode) [DX1000]
R5F21292SDSP@SOIC20 [DX1000]
R5F21292SDSP@SOIC20(single ISP) [DX0001]
R5F21292SDSP@SOIC20(single wire) [DX1000]
R5F21292SDSP@SOIC20(UART ISP) [DX0001]
R5F21292SDSP@SOIC20(UART mode) [DX1000]
R5F21292SJSP@SOIC20 [DX1000]
R5F21292SJSP@SOIC20(single ISP) [DX0001]
R5F21292SJSP@SOIC20(single wire) [DX1000]
R5F21292SJSP@SOIC20(UART ISP) [DX0001]
R5F21292SJSP@SOIC20(UART mode) [DX1000]
R5F21292SKSP@SOIC20 [DX1000]
R5F21292SKSP@SOIC20(single ISP) [DX0001]
R5F21292SKSP@SOIC20(single wire) [DX1000]
R5F21292SKSP@SOIC20(UART ISP) [DX0001]
R5F21292SKSP@SOIC20(UART mode) [DX1000]
R5F21292SNSP@SOIC20 [DX1000]
R5F21292SNSP@SOIC20(single ISP) [DX0001]
R5F21292SNSP@SOIC20(single wire) [DX1000]
R5F21292SNSP@SOIC20(UART ISP) [DX0001]
R5F21292SNSP@SOIC20(UART mode) [DX1000]
R5F21294DSP@SOIC20 [DX1000]
R5F21294DSP@SOIC20(single ISP) [DX0001]
R5F21294DSP@SOIC20(single wire) [DX1000]
R5F21294DSP@SOIC20(UART ISP) [DX0001]
R5F21294DSP@SOIC20(UART mode) [DX1000]
R5F21294JSP@SOIC20 [DX1000]
R5F21294JSP@SOIC20(single ISP) [DX0001]
R5F21294JSP@SOIC20(single wire) [DX1000]
R5F21294JSP@SOIC20(UART ISP) [DX0001]
R5F21294JSP@SOIC20(UART mode) [DX1000]
R5F21294KSP@SOIC20 [DX1000]
R5F21294KSP@SOIC20(single ISP) [DX0001]
R5F21294KSP@SOIC20(single wire) [DX1000]
R5F21294KSP@SOIC20(UART ISP) [DX0001]
R5F21294KSP@SOIC20(UART mode) [DX1000]
R5F21294NSP@SOIC20 [DX1000]
R5F21294NSP@SOIC20(single ISP) [DX0001]
R5F21294NSP@SOIC20(single wire) [DX1000]
R5F21294NSP@SOIC20(UART ISP) [DX0001]
R5F21294NSP@SOIC20(UART mode) [DX1000]
R5F21294SDSP@SOIC20 [DX1000]
R5F21294SDSP@SOIC20(single ISP) [DX0001]

R5F21294SDSP@SOIC20(single wire) [DX1000]
R5F21294SDSP@SOIC20(UART ISP) [DX0001]
R5F21294SDSP@SOIC20(UART mode) [DX1000]
R5F21294SJSP@SOIC20 [DX1000]
R5F21294SJSP@SOIC20(single ISP) [DX0001]
R5F21294SJSP@SOIC20(single wire) [DX1000]
R5F21294SJSP@SOIC20(UART ISP) [DX0001]
R5F21294SJSP@SOIC20(UART mode) [DX1000]
R5F21294SKSP@SOIC20 [DX1000]
R5F21294SKSP@SOIC20(single ISP) [DX0001]
R5F21294SKSP@SOIC20(single wire) [DX1000]
R5F21294SKSP@SOIC20(UART ISP) [DX0001]
R5F21294SKSP@SOIC20(UART mode) [DX1000]
R5F21294SNSP@SOIC20 [DX1000]
R5F21294SNSP@SOIC20(single ISP) [DX0001]
R5F21294SNSP@SOIC20(single wire) [DX1000]
R5F21294SNSP@SOIC20(UART ISP) [DX0001]
R5F21294SNSP@SOIC20(UART mode) [DX1000]
R5F212A7SDFA@TQFP64 [DX3044]
R5F212A7SDFA@TQFP64(single ISP) [DX0001]
R5F212A7SDFA@TQFP64(single wire) [DX3013]
R5F212A7SDFA@TQFP64(UART ISP) [DX0001]
R5F212A7SDFA@TQFP64(UART mode) [DX3013]
R5F212A7SDFP@TQFP64 [DX3011]
R5F212A7SDFP@TQFP64(single ISP) [DX0001]
R5F212A7SDFP@TQFP64(single wire) [DX3011]
R5F212A7SDFP@TQFP64(UART ISP) [DX0001]
R5F212A7SDFP@TQFP64(UART mode) [DX3011]
R5F212A7SNFA@TQFP64 [DX3044]
R5F212A7SNFA@TQFP64(single ISP) [DX0001]
R5F212A7SNFA@TQFP64(single wire) [DX3013]
R5F212A7SNFA@TQFP64(UART ISP) [DX0001]
R5F212A7SNFA@TQFP64(UART mode) [DX3013]
R5F212A7SNFP@TQFP64 [DX3011]
R5F212A7SNFP@TQFP64(single ISP) [DX0001]
R5F212A7SNFP@TQFP64(single wire) [DX3011]
R5F212A7SNFP@TQFP64(UART ISP) [DX0001]
R5F212A7SNFP@TQFP64(UART mode) [DX3011]
R5F212A8SDFA@TQFP64 [DX3044]
R5F212A8SDFA@TQFP64(single ISP) [DX0001]
R5F212A8SDFA@TQFP64(single wire) [DX3013]
R5F212A8SDFA@TQFP64(UART ISP) [DX0001]
R5F212A8SDFA@TQFP64(UART mode) [DX3013]
R5F212A8SDFP@TQFP64 [DX3011]
R5F212A8SDFP@TQFP64(single ISP) [DX0001]
R5F212A8SDFP@TQFP64(single wire) [DX3011]
R5F212A8SDFP@TQFP64(UART ISP) [DX0001]
R5F212A8SDFP@TQFP64(UART mode) [DX3011]

R5F212A8SNFA@TQFP64 [DX3044]
R5F212A8SNFA@TQFP64(single ISP) [DX0001]
R5F212A8SNFA@TQFP64(single wire) [DX3013]
R5F212A8SNFA@TQFP64(UART ISP) [DX0001]
R5F212A8SNFA@TQFP64(UART mode) [DX3013]
R5F212A8SNFP@TQFP64 [DX3011]
R5F212A8SNFP@TQFP64(single ISP) [DX0001]
R5F212A8SNFP@TQFP64(single wire) [DX3011]
R5F212A8SNFP@TQFP64(UART ISP) [DX0001]
R5F212A8SNFP@TQFP64(UART mode) [DX3011]
R5F212AASDFA@TQFP64 [DX3044]
R5F212AASDFA@TQFP64(single ISP) [DX0001]
R5F212AASDFA@TQFP64(single wire) [DX3013]
R5F212AASDFA@TQFP64(UART ISP) [DX0001]
R5F212AASDFA@TQFP64(UART mode) [DX3013]
R5F212AASDFP@TQFP64 [DX3011]
R5F212AASDFP@TQFP64(single ISP) [DX0001]
R5F212AASDFP@TQFP64(single wire) [DX3011]
R5F212AASDFP@TQFP64(UART ISP) [DX0001]
R5F212AASDFP@TQFP64(UART mode) [DX3011]
R5F212AASNFA@TQFP64 [DX3044]
R5F212AASNFA@TQFP64(single ISP) [DX0001]
R5F212AASNFA@TQFP64(single wire) [DX3013]
R5F212AASNFA@TQFP64(UART ISP) [DX0001]
R5F212AASNFA@TQFP64(UART mode) [DX3013]
R5F212AASNFP@TQFP64 [DX3011]
R5F212AASNFP@TQFP64(single ISP) [DX0001]
R5F212AASNFP@TQFP64(single wire) [DX3011]
R5F212AASNFP@TQFP64(UART ISP) [DX0001]
R5F212AASNFP@TQFP64(UART mode) [DX3011]
R5F212ACSDFA@TQFP64 [DX3044]
R5F212ACSDFA@TQFP64(single ISP) [DX0001]
R5F212ACSDFA@TQFP64(single wire) [DX3013]
R5F212ACSDFA@TQFP64(UART ISP) [DX0001]
R5F212ACSDFA@TQFP64(UART mode) [DX3013]
R5F212ACSDFP@TQFP64 [DX3011]
R5F212ACSDFP@TQFP64(single ISP) [DX0001]
R5F212ACSDFP@TQFP64(single wire) [DX3011]
R5F212ACSDFP@TQFP64(UART ISP) [DX0001]
R5F212ACSDFP@TQFP64(UART mode) [DX3011]
R5F212ACSNFA@TQFP64 [DX3044]
R5F212ACSNFA@TQFP64(single ISP) [DX0001]
R5F212ACSNFA@TQFP64(single wire) [DX3013]
R5F212ACSNFA@TQFP64(UART ISP) [DX0001]
R5F212ACSNFA@TQFP64(UART mode) [DX3013]
R5F212ACSNFP@TQFP64 [DX3011]
R5F212ACSNFP@TQFP64(single ISP) [DX0001]
R5F212ACSNFP@TQFP64(single wire) [DX3011]

R5F212ACSNFP@TQFP64(UART ISP) [DX0001]
R5F212ACSNFP@TQFP64(UART mode) [DX3011]
R5F212B7SDFA@TQFP64 [DX3044]
R5F212B7SDFA@TQFP64(single ISP) [DX0001]
R5F212B7SDFA@TQFP64(single wire) [DX3013]
R5F212B7SDFA@TQFP64(UART ISP) [DX0001]
R5F212B7SDFA@TQFP64(UART mode) [DX3013]
R5F212B7SDFP@TQFP64 [DX3011]
R5F212B7SDFP@TQFP64(single ISP) [DX0001]
R5F212B7SDFP@TQFP64(single wire) [DX3011]
R5F212B7SDFP@TQFP64(UART ISP) [DX0001]
R5F212B7SDFP@TQFP64(UART mode) [DX3011]
R5F212B7SNFA@TQFP64 [DX3044]
R5F212B7SNFA@TQFP64(single ISP) [DX0001]
R5F212B7SNFA@TQFP64(single wire) [DX3013]
R5F212B7SNFA@TQFP64(UART ISP) [DX0001]
R5F212B7SNFA@TQFP64(UART mode) [DX3013]
R5F212B7SNFP@TQFP64 [DX3011]
R5F212B7SNFP@TQFP64(single ISP) [DX0001]
R5F212B7SNFP@TQFP64(single wire) [DX3011]
R5F212B7SNFP@TQFP64(UART ISP) [DX0001]
R5F212B7SNFP@TQFP64(UART mode) [DX3011]
R5F212B8SDFA@TQFP64 [DX3044]
R5F212B8SDFA@TQFP64(single ISP) [DX0001]
R5F212B8SDFA@TQFP64(single wire) [DX3013]
R5F212B8SDFA@TQFP64(UART ISP) [DX0001]
R5F212B8SDFA@TQFP64(UART mode) [DX3013]
R5F212B8SDFP@TQFP64 [DX3011]
R5F212B8SDFP@TQFP64(single ISP) [DX0001]
R5F212B8SDFP@TQFP64(single wire) [DX3011]
R5F212B8SDFP@TQFP64(UART ISP) [DX0001]
R5F212B8SDFP@TQFP64(UART mode) [DX3011]
R5F212B8SNFA@TQFP64 [DX3044]
R5F212B8SNFA@TQFP64(single ISP) [DX0001]
R5F212B8SNFA@TQFP64(single wire) [DX3013]
R5F212B8SNFA@TQFP64(UART ISP) [DX0001]
R5F212B8SNFA@TQFP64(UART mode) [DX3013]
R5F212B8SNFP@TQFP64 [DX3011]
R5F212B8SNFP@TQFP64(single ISP) [DX0001]
R5F212B8SNFP@TQFP64(single wire) [DX3011]
R5F212B8SNFP@TQFP64(UART ISP) [DX0001]
R5F212B8SNFP@TQFP64(UART mode) [DX3011]
R5F212BASDFA@TQFP64 [DX3044]
R5F212BASDFA@TQFP64(single ISP) [DX0001]
R5F212BASDFA@TQFP64(single wire) [DX3013]
R5F212BASDFA@TQFP64(UART ISP) [DX0001]
R5F212BASDFA@TQFP64(UART mode) [DX3013]
R5F212BASDFP@TQFP64 [DX3011]

R5F212BASDFP@TQFP64(single ISP) [DX0001]
R5F212BASDFP@TQFP64(single wire) [DX3011]
R5F212BASDFP@TQFP64(UART ISP) [DX0001]
R5F212BASDFP@TQFP64(UART mode) [DX3011]
R5F212BASNFA@TQFP64 [DX3044]
R5F212BASNFA@TQFP64(single ISP) [DX0001]
R5F212BASNFA@TQFP64(single wire) [DX3013]
R5F212BASNFA@TQFP64(UART ISP) [DX0001]
R5F212BASNFA@TQFP64(UART mode) [DX3013]
R5F212BASNFP@TQFP64 [DX3011]
R5F212BASNFP@TQFP64(single ISP) [DX0001]
R5F212BASNFP@TQFP64(single wire) [DX3011]
R5F212BASNFP@TQFP64(UART ISP) [DX0001]
R5F212BASNFP@TQFP64(UART mode) [DX3011]
R5F212BCSDFA@TQFP64 [DX3044]
R5F212BCSDFA@TQFP64(single ISP) [DX0001]
R5F212BCSDFA@TQFP64(single wire) [DX3013]
R5F212BCSDFA@TQFP64(UART ISP) [DX0001]
R5F212BCSDFA@TQFP64(UART mode) [DX3013]
R5F212BCSDFP@TQFP64 [DX3011]
R5F212BCSDFP@TQFP64(single ISP) [DX0001]
R5F212BCSDFP@TQFP64(single wire) [DX3011]
R5F212BCSDFP@TQFP64(UART ISP) [DX0001]
R5F212BCSDFP@TQFP64(UART mode) [DX3011]
R5F212BCSNFA@TQFP64 [DX3044]
R5F212BCSNFA@TQFP64(single ISP) [DX0001]
R5F212BCSNFA@TQFP64(single wire) [DX3013]
R5F212BCSNFA@TQFP64(UART ISP) [DX0001]
R5F212BCSNFA@TQFP64(UART mode) [DX3013]
R5F212BCSNFP@TQFP64 [DX3011]
R5F212BCSNFP@TQFP64(single ISP) [DX0001]
R5F212BCSNFP@TQFP64(single wire) [DX3011]
R5F212BCSNFP@TQFP64(UART ISP) [DX0001]
R5F212BCSNFP@TQFP64(UART mode) [DX3011]
R5F212C7SDFP@TQFP80 [DX3016]
R5F212C7SDFP@TQFP80(single ISP) [DX0001]
R5F212C7SDFP@TQFP80(single wire) [DX3016]
R5F212C7SDFP@TQFP80(UART ISP) [DX0001]
R5F212C7SDFP@TQFP80(UART mode) [DX3016]
R5F212C7SNFP@TQFP80 [DX3016]
R5F212C7SNFP@TQFP80(single ISP) [DX0001]
R5F212C7SNFP@TQFP80(single wire) [DX3016]
R5F212C7SNFP@TQFP80(UART ISP) [DX0001]
R5F212C7SNFP@TQFP80(UART mode) [DX3016]
R5F212C8SDFP@TQFP80 [DX3016]
R5F212C8SDFP@TQFP80(single ISP) [DX0001]
R5F212C8SDFP@TQFP80(single wire) [DX3016]
R5F212C8SDFP@TQFP80(UART ISP) [DX0001]

R5F212C8SDFP@TQFP80(UART mode) [DX3016]
R5F212C8SNFP@TQFP80 [DX3016]
R5F212C8SNFP@TQFP80(single ISP) [DX0001]
R5F212C8SNFP@TQFP80(single wire) [DX3016]
R5F212C8SNFP@TQFP80(UART ISP) [DX0001]
R5F212C8SNFP@TQFP80(UART mode) [DX3016]
R5F212CASDFP@TQFP80 [DX3016]
R5F212CASDFP@TQFP80(single ISP) [DX0001]
R5F212CASDFP@TQFP80(single wire) [DX3016]
R5F212CASDFP@TQFP80(UART ISP) [DX0001]
R5F212CASDFP@TQFP80(UART mode) [DX3016]
R5F212CASNFP@TQFP80 [DX3016]
R5F212CASNFP@TQFP80(single ISP) [DX0001]
R5F212CASNFP@TQFP80(single wire) [DX3016]
R5F212CASNFP@TQFP80(UART ISP) [DX0001]
R5F212CASNFP@TQFP80(UART mode) [DX3016]
R5F212CCSDFP@TQFP80 [DX3016]
R5F212CCSDFP@TQFP80(single ISP) [DX0001]
R5F212CCSDFP@TQFP80(single wire) [DX3016]
R5F212CCSDFP@TQFP80(UART ISP) [DX0001]
R5F212CCSDFP@TQFP80(UART mode) [DX3016]
R5F212CCSNFP@TQFP80 [DX3016]
R5F212CCSNFP@TQFP80(single ISP) [DX0001]
R5F212CCSNFP@TQFP80(single wire) [DX3016]
R5F212CCSNFP@TQFP80(UART ISP) [DX0001]
R5F212CCSNFP@TQFP80(UART mode) [DX3016]
R5F212D7SDFP@TQFP80 [DX3016]
R5F212D7SDFP@TQFP80(single ISP) [DX0001]
R5F212D7SDFP@TQFP80(single wire) [DX3016]
R5F212D7SDFP@TQFP80(UART ISP) [DX0001]
R5F212D7SDFP@TQFP80(UART mode) [DX3016]
R5F212D7SNFP@TQFP80 [DX3016]
R5F212D7SNFP@TQFP80(single ISP) [DX0001]
R5F212D7SNFP@TQFP80(single wire) [DX3016]
R5F212D7SNFP@TQFP80(UART ISP) [DX0001]
R5F212D7SNFP@TQFP80(UART mode) [DX3016]
R5F212D8SDFP@TQFP80 [DX3016]
R5F212D8SDFP@TQFP80(single ISP) [DX0001]
R5F212D8SDFP@TQFP80(single wire) [DX3016]
R5F212D8SDFP@TQFP80(UART ISP) [DX0001]
R5F212D8SDFP@TQFP80(UART mode) [DX3016]
R5F212D8SNFP@TQFP80 [DX3016]
R5F212D8SNFP@TQFP80(single ISP) [DX0001]
R5F212D8SNFP@TQFP80(single wire) [DX3016]
R5F212D8SNFP@TQFP80(UART ISP) [DX0001]
R5F212D8SNFP@TQFP80(UART mode) [DX3016]
R5F212DASDFP@TQFP80 [DX3016]
R5F212DASDFP@TQFP80(single ISP) [DX0001]

R5F212DASDFP@TQFP80(single wire) [DX3016]
R5F212DASDFP@TQFP80(UART ISP) [DX0001]
R5F212DASDFP@TQFP80(UART mode) [DX3016]
R5F212DASNFP@TQFP80 [DX3016]
R5F212DASNFP@TQFP80(single ISP) [DX0001]
R5F212DASNFP@TQFP80(single wire) [DX3016]
R5F212DASNFP@TQFP80(UART ISP) [DX0001]
R5F212DASNFP@TQFP80(UART mode) [DX3016]
R5F212DCSDFP@TQFP80 [DX3016]
R5F212DCSDFP@TQFP80(single ISP) [DX0001]
R5F212DCSDFP@TQFP80(single wire) [DX3016]
R5F212DCSDFP@TQFP80(UART ISP) [DX0001]
R5F212DCSDFP@TQFP80(UART mode) [DX3016]
R5F212DCSNFP@TQFP80 [DX3016]
R5F212DCSNFP@TQFP80(single ISP) [DX0001]
R5F212DCSNFP@TQFP80(single wire) [DX3016]
R5F212DCSNFP@TQFP80(UART ISP) [DX0001]
R5F212DCSNFP@TQFP80(UART mode) [DX3016]
R5F212G4SDFP@QFP32 [DX3061]
R5F212G4SDFP@QFP32(single ISP) [DX0001]
R5F212G4SDFP@QFP32(single wire) [DX3061]
R5F212G4SNFP@QFP32 [DX3061]
R5F212G4SNFP@QFP32(single ISP) [DX0001]
R5F212G4SNFP@QFP32(single wire) [DX3061]
R5F212G5SDFP@QFP32 [DX3061]
R5F212G5SDFP@QFP32(single ISP) [DX0001]
R5F212G5SDFP@QFP32(single wire) [DX3061]
R5F212G5SNFP@QFP32 [DX3061]
R5F212G5SNFP@QFP32(single ISP) [DX0001]
R5F212G5SNFP@QFP32(single wire) [DX3061]
R5F212G6SDFP@QFP32 [DX3061]
R5F212G6SDFP@QFP32(single ISP) [DX0001]
R5F212G6SDFP@QFP32(single wire) [DX3061]
R5F212G6SNFP@QFP32 [DX3061]
R5F212G6SNFP@QFP32(single ISP) [DX0001]
R5F212G6SNFP@QFP32(single wire) [DX3061]
R5F212H1SDSP@TSSOP20 [DX1000]
R5F212H1SDSP@TSSOP20(single ISP) [DX0001]
R5F212H1SDSP@TSSOP20(single) [DX1000]
R5F212H1SNSP@TSSOP20 [DX1000]
R5F212H1SNSP@TSSOP20(single ISP) [DX0001]
R5F212H1SNSP@TSSOP20(single) [DX1000]
R5F212H2SDSP@TSSOP20 [DX1000]
R5F212H2SDSP@TSSOP20(single ISP) [DX0001]
R5F212H2SDSP@TSSOP20(single) [DX1000]
R5F212H2SNSP@TSSOP20 [DX1000]
R5F212H2SNSP@TSSOP20(single ISP) [DX0001]
R5F212H2SNSP@TSSOP20(single) [DX1000]

R5F212J0SDSP@TSSOP20 [DX1000]
R5F212J0SDSP@TSSOP20(single ISP) [DX0001]
R5F212J0SDSP@TSSOP20(single) [DX1000]
R5F212J0SNSP@TSSOP20 [DX1000]
R5F212J0SNSP@TSSOP20(single ISP) [DX0001]
R5F212J0SNSP@TSSOP20(single) [DX1000]
R5F212J1SDSP@TSSOP20 [DX1000]
R5F212J1SDSP@TSSOP20(single ISP) [DX0001]
R5F212J1SDSP@TSSOP20(single) [DX1000]
R5F212J1SNSP@TSSOP20 [DX1000]
R5F212J1SNSP@TSSOP20(single ISP) [DX0001]
R5F212J1SNSP@TSSOP20(single) [DX1000]
R5F212K2SDFP@QFP32 [DX3061]
R5F212K2SDFP@QFP32(single ISP) [DX0001]
R5F212K2SDFP@QFP32(single wire) [DX3050]
R5F212K2SDFP@QFP32(UART ISP) [DX0001]
R5F212K2SDFP@QFP32(UART mode) [DX3050]
R5F212K2SNFP@QFP32 [DX3061]
R5F212K2SNFP@QFP32(single ISP) [DX0001]
R5F212K2SNFP@QFP32(single wire) [DX3050]
R5F212K2SNFP@QFP32(UART ISP) [DX0001]
R5F212K2SNFP@QFP32(UART mode) [DX3050]
R5F212K4SDFP@QFP32 [DX3061]
R5F212K4SDFP@QFP32(single ISP) [DX0001]
R5F212K4SDFP@QFP32(single wire) [DX3050]
R5F212K4SDFP@QFP32(UART ISP) [DX0001]
R5F212K4SDFP@QFP32(UART mode) [DX3050]
R5F212K4SNFP@QFP32 [DX3061]
R5F212K4SNFP@QFP32(single ISP) [DX0001]
R5F212K4SNFP@QFP32(single wire) [DX3050]
R5F212K4SNFP@QFP32(UART ISP) [DX0001]
R5F212K4SNFP@QFP32(UART mode) [DX3050]
R5F212L2SDFP@QFP32 [DX3061]
R5F212L2SDFP@QFP32(single ISP) [DX0001]
R5F212L2SDFP@QFP32(single wire) [DX3050]
R5F212L2SDFP@QFP32(UART ISP) [DX0001]
R5F212L2SDFP@QFP32(UART mode) [DX3050]
R5F212L2SNFP@QFP32 [DX3061]
R5F212L2SNFP@QFP32(single ISP) [DX0001]
R5F212L2SNFP@QFP32(single wire) [DX3050]
R5F212L2SNFP@QFP32(UART ISP) [DX0001]
R5F212L2SNFP@QFP32(UART mode) [DX3050]
R5F212L4SDFP@QFP32 [DX3061]
R5F212L4SDFP@QFP32(single ISP) [DX0001]
R5F212L4SDFP@QFP32(single wire) [DX3050]
R5F212L4SDFP@QFP32(UART ISP) [DX0001]
R5F212L4SDFP@QFP32(UART mode) [DX3050]
R5F212L4SNFP@QFP32 [DX3061]

R5F212L4SNFP@QFP32(single ISP) [DX0001]
R5F212L4SNFP@QFP32(single wire) [DX3050]
R5F212L4SNFP@QFP32(UART ISP) [DX0001]
R5F212L4SNFP@QFP32(UART mode) [DX3050]

R5F21331ADFP [DX3001]	R5F21331ANFP [DX3001]
R5F21331CDFP [DX3001]	R5F21331CNFP [DX3001]
R5F21331DDFP [DX3001]	R5F21331DNFP [DX3001]
R5F21331MDFP [DX3001]	R5F21331MNFP [DX3001]
R5F21332ADFP [DX3001]	R5F21332ANFP [DX3001]
R5F21332CDFP [DX3001]	R5F21332CNFP [DX3001]
R5F21332DDFP [DX3001]	R5F21332DNFP [DX3001]
R5F21332MDFP [DX3001]	R5F21332MNFP [DX3001]
R5F21334ADFP [DX3001]	R5F21334ANFP [DX3001]
R5F21334CDFP [DX3001]	R5F21334CNFP [DX3001]
R5F21334DDFP [DX3001]	R5F21334DNFP [DX3001]
R5F21334MDFP [DX3001]	R5F21334MNFP [DX3001]
R5F21334TDFP [DX3001]	R5F21334TNFP [DX3001]
R5F21335ADFP [DX3001]	R5F21335ANFP [DX3001]
R5F21335CDFP [DX3001]	R5F21335CNFP [DX3001]
R5F21335DDFP [DX3001]	R5F21335DNFP [DX3001]
R5F21335MDFP [DX3001]	R5F21335MNFP [DX3001]
R5F21335TDFP [DX3001]	R5F21335TNFP [DX3001]
R5F21336ADFP [DX3001]	R5F21336ANFP [DX3001]
R5F21336CDFP [DX3001]	R5F21336CNFP [DX3001]
R5F21336DDFP [DX3001]	R5F21336DNFP [DX3001]
R5F21336MDFP [DX3001]	R5F21336MNFP [DX3001]
R5F21336MYFP@QFP32 [DX3001]	R5F21336TDFP [DX3001]
R5F21336TNFP [DX3001]	R5F21346EJFP@QFP48 [DX3007]
R5F21346EKFP@QFP48 [DX3007]	R5F21346FJFP@QFP48 [DX3007]
R5F21346FKFP@QFP48 [DX3007]	R5F21346GJFP@QFP48 [DX3007]
R5F21346GKFP@QFP48 [DX3007]	R5F21346HJFP@QFP48 [DX3007]
R5F21346HKFP@QFP48 [DX3007]	R5F21346WJFP [DX3007]
R5F21346WKFP [DX3007]	R5F21346XJFP [DX3007]
R5F21346XKFP [DX3007]	R5F21347EJFP@QFP48 [DX3007]
R5F21347EKFP@QFP48 [DX3007]	R5F21347FJFP@QFP48 [DX3007]
R5F21347FKFP@QFP48 [DX3007]	R5F21347GJFP@QFP48 [DX3007]
R5F21347GKFP@QFP48 [DX3007]	R5F21347HJFP@QFP48 [DX3007]
R5F21347HKFP@QFP48 [DX3007]	R5F21347WJFP [DX3007]
R5F21347WKFP [DX3007]	R5F21347XJFP [DX3007]
R5F21347XKFP [DX3007]	R5F21348EJFP@QFP48 [DX3007]
R5F21348EKFP@QFP48 [DX3007]	R5F21348FJFP@QFP48 [DX3007]
R5F21348FKFP@QFP48 [DX3007]	R5F21348GJFP@QFP48 [DX3007]
R5F21348GKFP@QFP48 [DX3007]	R5F21348HJFP@QFP48 [DX3007]
R5F21348HKFP@QFP48 [DX3007]	R5F21348WJFP [DX3007]
R5F21348WKFP [DX3007]	R5F21348XJFP [DX3007]
R5F21348XKFP [DX3007]	R5F2134AEJFP@QFP48 [DX3007]
R5F2134AEKFP@QFP48 [DX3007]	R5F2134AFJFP@QFP48 [DX3007]
R5F2134AFKFP@QFP48 [DX3007]	R5F2134AGJFP@QFP48 [DX3007]

R5F2134AGKFP@QFP48 [DX3007]
R5F2134AHJFP@QFP48 [DX3007]
R5F2134AHKFP@QFP48 [DX3007]
R5F2134AWJFP [DX3007]
R5F2134AWKFP [DX3007]
R5F2134AXJFP [DX3007]
R5F2134AXKFP [DX3007]
R5F2134CEJFP@QFP48 [DX3007]
R5F2134CEKFP@QFP48 [DX3007]
R5F2134CFJFP@QFP48 [DX3007]
R5F2134CFKFP@QFP48 [DX3007]
R5F2134CGJFP@QFP48 [DX3007]
R5F2134CGKFP@QFP48 [DX3007]
R5F2134CHJFP@QFP48 [DX3007]
R5F2134CHKFP@QFP48 [DX3007]
R5F2134CWJFP [DX3007]
R5F2134CWKFP@QFP48 [DX3007]
R5F2134CWKFP@QFP48(left down) [DX3007]
R5F2134CXJFP [DX3007]
R5F2134CXKFP [DX3007]
R5F21354ADFP [DX3010]
R5F21354ADFP@QFP52(single wire) [DX3010]
R5F21354ANFP [DX3010]
R5F21354ANFP@QFP52(single wire) [DX3010]
R5F21354BDFP@QFP52(single wire) [DX3010]
R5F21354BNFP@QFP52(single wire) [DX3010]
R5F21354CDFP [DX3010]
R5F21354CDFP@QFP52(single wire) [DX3010]
R5F21354CNFP [DX3010]
R5F21354CNFP@QFP52(single wire) [DX3010]
R5F21354CYFP [DX3010]
R5F21354MDFP [DX3010]
R5F21354MNFP [DX3010]
R5F21355ADFP [DX3010]
R5F21355ADFP@QFP52(single wire) [DX3010]
R5F21355ANFP [DX3010]
R5F21355ANFP@QFP52(single wire) [DX3010]
R5F21355BDFP@QFP52(single wire) [DX3010]
R5F21355BNFP@QFP52(single wire) [DX3010]
R5F21355CDFP [DX3010]
R5F21355CDFP@QFP52(single wire) [DX3010]
R5F21355CNFP [DX3010]
R5F21355CNFP@QFP52(single wire) [DX3010]
R5F21355CYFP [DX3010]
R5F21355MDFP [DX3010]
R5F21355MNFP [DX3010]
R5F21356ADFP [DX3010]
R5F21356ADFP@QFP52(single wire) [DX3010]
R5F21356ANFP [DX3010]
R5F21356ANFP@QFP52(single wire) [DX3010]
R5F21356BDFP@QFP52(single wire) [DX3010]
R5F21356BNFP@QFP52(single wire) [DX3010]
R5F21356CDFP [DX3010]
R5F21356CDFP@QFP52(single wire) [DX3010]
R5F21356CNFP [DX3010]
R5F21356CNFP@QFP52(single wire) [DX3010]
R5F21356CYFP [DX3010]
R5F21356MDFP [DX3010]
R5F21356MNFP [DX3010]
R5F21357ADFP [DX3010]
R5F21357ADFP@QFP52(single wire) [DX3010]
R5F21357ANFP [DX3010]
R5F21357ANFP@QFP52(single wire) [DX3010]

R5F21357BDFP@QFP52(single wire) [DX3010]
R5F21357BNFP@QFP52(single wire) [DX3010]
R5F21357CDFP [DX3010]
R5F21357CDFP@QFP52(single wire) [DX3010]
R5F21357CNFP [DX3010]
R5F21357CNFP@QFP52(single wire) [DX3010]
R5F21357CYFP [DX3010]
R5F21357CYFP@QFP52(single wire) [DX3010]
R5F21357MDFP [DX3010]
R5F21357MNFP [DX3010]
R5F21358ADFP [DX3010]
R5F21358ADFP@QFP52(single wire) [DX3010]
R5F21358ANFP [DX3010]
R5F21358ANFP@QFP52(single wire) [DX3010]
R5F21358BDFP@QFP52(single wire) [DX3010]
R5F21358BNFP@QFP52(single wire) [DX3010]
R5F21358CDFP [DX3010]
R5F21358CDFP@QFP52(single wire) [DX3010]
R5F21358CNFP [DX3010]
R5F21358CNFP@QFP52(single wire) [DX3010]
R5F21358CYFP [DX3010]
R5F21358MDFP [DX3010]
R5F21358MNFP [DX3010]
R5F2135AADFP [DX3010]
R5F2135AADFP@QFP52(single wire) [DX3010]
R5F2135AANFP [DX3010]
R5F2135AANFP@QFP52(single wire) [DX3010]
R5F2135ABDFP@QFP52(single wire) [DX3010]
R5F2135ABNFP@QFP52(single wire) [DX3010]
R5F2135ACDFP [DX3010]
R5F2135ACDFP@QFP52(single wire) [DX3010]
R5F2135ACNFP [DX3010]
R5F2135ACNFP@QFP52(single wire) [DX3010]
R5F2135ACYFP [DX3010]
R5F2135AMDFP [DX3010]
R5F2135AMNFP [DX3010]
R5F2135CADFP [DX3010]
R5F2135CADFP@QFP52(single wire) [DX3010]
R5F2135CANFP [DX3010]
R5F2135CANFP@QFP52(single wire) [DX3010]
R5F2135CBDFP@QFP52(single wire) [DX3010]
R5F2135CBNFP@QFP52(single wire) [DX3010]
R5F2135CCDFP [DX3010]
R5F2135CCDFP@QFP52(single wire) [DX3010]
R5F2135CCNFP [DX3010]
R5F2135CCNFP@QFP52(single wire) [DX3010]
R5F2135CCYFP [DX3010]
R5F2135CMDFP [DX3010]
R5F2135CMNFP [DX3010]
R5F21364ADFA [DX3100]
R5F21364ADFP [DX3011]
R5F21364ANFA [DX3100]
R5F21364ANFP [DX3011]
R5F21364CDFA [DX3100]
R5F21364CDFP [DX3011]
R5F21364CNFA [DX3100]
R5F21364CNFP [DX3011]
R5F21365ADFA [DX3100]
R5F21365ADFP [DX3011]
R5F21365ANFA [DX3100]

R5F21365ANFP [DX3011]　　R5F21365CDFA [DX3100]
R5F21365CDFP [DX3011]　　R5F21365CNFA [DX3100]
R5F21365CNFP [DX3011]　　R5F21366ADFA [DX3100]
R5F21366ADFP [DX3011]　　R5F21366ANFA [DX3100]
R5F21366ANFP [DX3011]　　R5F21366CDFA [DX3100]
R5F21366CDFP [DX3011]　　R5F21366CNFA [DX3100]
R5F21366CNFP [DX3011]　　R5F21367ADFA [DX3100]
R5F21367ADFP [DX3011]　　R5F21367ANFA [DX3100]
R5F21367ANFP [DX3011]　　R5F21367CDFA [DX3100]
R5F21367CDFP [DX3011]　　R5F21367CNFA [DX3100]
R5F21367CNFP [DX3011]　　R5F21368ADFA [DX3100]
R5F21368ADFP [DX3011]　　R5F21368ANFA [DX3100]
R5F21368ANFP [DX3011]　　R5F21368CDFA [DX3100]
R5F21368CDFP [DX3011]　　R5F21368CNFA [DX3100]
R5F21368CNFP [DX3011]
R5F21368SDFA@QFP64(single wire) [DX3014]
R5F21368SDFP@QFP64(single wire) [DX3011]
R5F21368SNFA@QFP64(single wire) [DX3014]
R5F21368SNFP@QFP64(single wire) [DX3011]
R5F2136AADFA [DX3100]　　R5F2136AADFP [DX3011]
R5F2136AANFA [DX3100]　　R5F2136AANFP [DX3011]
R5F2136ACDFA [DX3100]　　R5F2136ACDFP [DX3011]
R5F2136ACNFA [DX3100]　　R5F2136ACNFP [DX3011]
R5F2136ASDFA@QFP64(single wire) [DX3014]
R5F2136ASDFP@QFP64(single wire) [DX3011]
R5F2136ASNFA@QFP64(single wire) [DX3014]
R5F2136ASNFP@QFP64(single wire) [DX3011]
R5F2136CADFA [DX3100]　　R5F2136CADFP [DX3011]
R5F2136CANFA [DX3100]　　R5F2136CANFP [DX3011]
R5F2136CCDFA [DX3100]　　R5F2136CCDFP [DX3011]
R5F2136CCNFA [DX3100]　　R5F2136CCNFP [DX3011]
R5F2136CSDFA@QFP64(single wire) [DX3014]
R5F2136CSDFP@QFP64(single wire) [DX3011]
R5F2136CSNFA@QFP64(single wire) [DX3014]
R5F2136CSNFP@QFP64(single wire) [DX3011]
R5F21388SDFP(single wire) [DX3016]
R5F21388SNFP(single wire) [DX3016]
R5F2138ASDFP(single wire) [DX3016]
R5F2138ASNFP(single wire) [DX3016]
R5F2138CSDFP(single wire) [DX3016]
R5F2138CSNFP(single wire) [DX3016]
R5F213G1DDSP [DX1095]　　R5F213G1DNSP [DX1095]
R5F213G2DDSP [DX1095]　　R5F213G2DNSP [DX1095]
R5F213G4DDSP [DX1095]　　R5F213G4DNSP [DX1095]
R5F213G5DDSP [DX1095]　　R5F213G5DNSP [DX1095]
R5F213G6DDSP [DX1095]　　R5F213G6DNSP [DX1095]
R5F2L357ADFP@QFP52 [DX3010]
R5F2L357ADFP@QFP52(single wire) [DX3010]

R5F2L357ANFP@QFP52 [DX3010]
R5F2L357ANFP@QFP52(single wire) [DX3010]
R5F2L357BDFP@QFP52 [DX3010]
R5F2L357BDFP@QFP52(single wire) [DX3010]
R5F2L357BNFP@QFP52 [DX3010]
R5F2L357BNFP@QFP52(single wire) [DX3010]
R5F2L357CDFP@QFP52 [DX3010]
R5F2L357CDFP@QFP52(single wire) [DX3010]
R5F2L357CNFP@QFP52 [DX3010]
R5F2L357CNFP@QFP52(single wire) [DX3010]
R5F2L358ADFP@QFP52 [DX3010]
R5F2L358ADFP@QFP52(single wire) [DX3010]
R5F2L358ANFP@QFP52 [DX3010]
R5F2L358ANFP@QFP52(single wire) [DX3010]
R5F2L358BDFP@QFP52 [DX3010]
R5F2L358BDFP@QFP52(single wire) [DX3010]
R5F2L358BNFP@QFP52 [DX3010]
R5F2L358BNFP@QFP52(single wire) [DX3010]
R5F2L358CDFP@QFP52 [DX3010]
R5F2L358CDFP@QFP52(single wire) [DX3010]
R5F2L358CNFP@QFP52 [DX3010]
R5F2L358CNFP@QFP52(single wire) [DX3010]
R5F2L35AADFP@QFP52 [DX3010]
R5F2L35AADFP@QFP52(single wire) [DX3010]
R5F2L35AANFP@QFP52 [DX3010]
R5F2L35AANFP@QFP52(single wire) [DX3010]
R5F2L35ABDFP@QFP52 [DX3010]
R5F2L35ABDFP@QFP52(single wire) [DX3010]
R5F2L35ABNFP@QFP52 [DX3010]
R5F2L35ABNFP@QFP52(single wire) [DX3010]
R5F2L35ACDFP@QFP52 [DX3010]
R5F2L35ACDFP@QFP52(single wire) [DX3010]
R5F2L35ACNFP@QFP52 [DX3010]
R5F2L35ACNFP@QFP52(single wire) [DX3010]
R5F2L35CADFP@QFP52 [DX3010]
R5F2L35CADFP@QFP52(single wire) [DX3010]
R5F2L35CANFP@QFP52 [DX3010]
R5F2L35CANFP@QFP52(single wire) [DX3010]
R5F2L35CBDFP@QFP52 [DX3010]
R5F2L35CBDFP@QFP52(single wire) [DX3010]
R5F2L35CBNFP@QFP52 [DX3010]
R5F2L35CBNFP@QFP52(single wire) [DX3010]
R5F2L35CCDFP@QFP52 [DX3010]
R5F2L35CCDFP@QFP52(single wire) [DX3010]
R5F2L35CCNFP@QFP52 [DX3010]
R5F2L35CCNFP@QFP52(single wire) [DX3010]
R5F2L367ADFA@QFP64 [DX3013]
R5F2L367ADFA@QFP64(single wire) [DX3013]

R5F2L367ADFP@QFP64 [DX3011]
R5F2L367ADFP@QFP64(single wire) [DX3011]
R5F2L367ANFA@QFP64 [DX3013]
R5F2L367ANFA@QFP64(single wire) [DX3013]
R5F2L367ANFP@QFP64 [DX3011]
R5F2L367ANFP@QFP64(single wire) [DX3011]
R5F2L367BDFA@QFP64 [DX3013]
R5F2L367BDFA@QFP64(single wire) [DX3013]
R5F2L367BDFP@QFP64 [DX3011]
R5F2L367BDFP@QFP64(single wire) [DX3011]
R5F2L367BNFA@QFP64 [DX3013]
R5F2L367BNFA@QFP64(single wire) [DX3013]
R5F2L367BNFP@QFP64 [DX3011]
R5F2L367BNFP@QFP64(single wire) [DX3011]
R5F2L367CDFA@QFP64 [DX3013]
R5F2L367CDFA@QFP64(single wire) [DX3013]
R5F2L367CDFP@QFP64 [DX3011]
R5F2L367CDFP@QFP64(single wire) [DX3011]
R5F2L367CNFA@QFP64 [DX3013]
R5F2L367CNFA@QFP64(single wire) [DX3013]
R5F2L367CNFP@QFP64 [DX3011]
R5F2L367CNFP@QFP64(single wire) [DX3011]
R5F2L368ADFA@QFP64 [DX3013]
R5F2L368ADFA@QFP64(single wire) [DX3013]
R5F2L368ADFP@QFP64 [DX3011]
R5F2L368ADFP@QFP64(single wire) [DX3011]
R5F2L368ANFA@QFP64 [DX3013]
R5F2L368ANFA@QFP64(single wire) [DX3013]
R5F2L368ANFP@QFP64 [DX3011]
R5F2L368ANFP@QFP64(single wire) [DX3011]
R5F2L368BDFA@QFP64 [DX3013]
R5F2L368BDFA@QFP64(single wire) [DX3013]
R5F2L368BDFP@QFP64 [DX3011]
R5F2L368BDFP@QFP64(single wire) [DX3011]
R5F2L368BNFA@QFP64 [DX3013]
R5F2L368BNFA@QFP64(single wire) [DX3013]
R5F2L368BNFP@QFP64 [DX3011]
R5F2L368BNFP@QFP64(single wire) [DX3011]
R5F2L368CDFA@QFP64 [DX3013]
R5F2L368CDFA@QFP64(single wire) [DX3013]
R5F2L368CDFP@QFP64 [DX3011]
R5F2L368CDFP@QFP64(single wire) [DX3011]
R5F2L368CNFA@QFP64 [DX3013]
R5F2L368CNFA@QFP64(single wire) [DX3013]
R5F2L368CNFP@QFP64 [DX3011]
R5F2L368CNFP@QFP64(single wire) [DX3011]
R5F2L36AADFA@QFP64 [DX3013]
R5F2L36AADFA@QFP64(single wire) [DX3013]

R5F2L36AADFP@QFP64 [DX3011]
R5F2L36AADFP@QFP64(single wire) [DX3011]
R5F2L36AANFA@QFP64 [DX3013]
R5F2L36AANFA@QFP64(single wire) [DX3013]
R5F2L36AANFP@QFP64 [DX3011]
R5F2L36AANFP@QFP64(single wire) [DX3011]
R5F2L36ABDFA@QFP64 [DX3013]
R5F2L36ABDFA@QFP64(single wire) [DX3013]
R5F2L36ABDFP@QFP64 [DX3011]
R5F2L36ABDFP@QFP64(single wire) [DX3011]
R5F2L36ABNFA@QFP64 [DX3013]
R5F2L36ABNFA@QFP64(single wire) [DX3013]
R5F2L36ABNFP@QFP64 [DX3011]
R5F2L36ABNFP@QFP64(single wire) [DX3011]
R5F2L36ACDFA@QFP64 [DX3013]
R5F2L36ACDFA@QFP64(single wire) [DX3013]
R5F2L36ACDFP@QFP64 [DX3011]
R5F2L36ACDFP@QFP64(single wire) [DX3011]
R5F2L36ACNFA@QFP64 [DX3013]
R5F2L36ACNFA@QFP64(single wire) [DX3013]
R5F2L36ACNFP@QFP64 [DX3011]
R5F2L36ACNFP@QFP64(single wire) [DX3011]
R5F2L36CADFA@QFP64 [DX3013]
R5F2L36CADFA@QFP64(single wire) [DX3013]
R5F2L36CADFP@QFP64 [DX3011]
R5F2L36CADFP@QFP64(single wire) [DX3011]
R5F2L36CANFA@QFP64 [DX3013]
R5F2L36CANFA@QFP64(single wire) [DX3013]
R5F2L36CANFP@QFP64 [DX3011]
R5F2L36CANFP@QFP64(single wire) [DX3011]
R5F2L36CBDFA@QFP64 [DX3013]
R5F2L36CBDFA@QFP64(single wire) [DX3013]
R5F2L36CBDFP@QFP64 [DX3011]
R5F2L36CBDFP@QFP64(single wire) [DX3011]
R5F2L36CBNFA@QFP64 [DX3013]
R5F2L36CBNFA@QFP64(single wire) [DX3013]
R5F2L36CBNFP@QFP64 [DX3011]
R5F2L36CBNFP@QFP64(single wire) [DX3011]
R5F2L36CCDFA@QFP64 [DX3013]
R5F2L36CCDFA@QFP64(single wire) [DX3013]
R5F2L36CCDFP@QFP64 [DX3011]
R5F2L36CCDFP@QFP64(single wire) [DX3011]
R5F2L36CCNFA@QFP64 [DX3013]
R5F2L36CCNFA@QFP64(single wire) [DX3013]
R5F2L36CCNFP@QFP64 [DX3011]
R5F2L36CCNFP@QFP64(single wire) [DX3011]
R5F2L387ADFA@QFP80 [DX3018]
R5F2L387ADFA@QFP80(single wire) [DX3018]

R5F2L387ADFP@QFP80 [DX3016]
R5F2L387ADFP@QFP80(single wire) [DX3016]
R5F2L387ANFA@QFP80 [DX3018]
R5F2L387ANFA@QFP80(single wire) [DX3018]
R5F2L387ANFP@QFP80 [DX3016]
R5F2L387ANFP@QFP80(single wire) [DX3016]
R5F2L387BDFA@QFP80 [DX3018]
R5F2L387BDFA@QFP80(single wire) [DX3018]
R5F2L387BDFP@QFP80 [DX3016]
R5F2L387BDFP@QFP80(single wire) [DX3016]
R5F2L387BNFA@QFP80 [DX3018]
R5F2L387BNFA@QFP80(single wire) [DX3018]
R5F2L387BNFP@QFP80 [DX3016]
R5F2L387BNFP@QFP80(single wire) [DX3016]
R5F2L387CDFA@QFP80 [DX3018]
R5F2L387CDFA@QFP80(single wire) [DX3018]
R5F2L387CDFP@QFP80 [DX3016]
R5F2L387CDFP@QFP80(single wire) [DX3016]
R5F2L387CNFA@QFP80 [DX3018]
R5F2L387CNFA@QFP80(single wire) [DX3018]
R5F2L387CNFP@QFP80 [DX3016]
R5F2L387CNFP@QFP80(single wire) [DX3016]
R5F2L388ADFA@QFP80 [DX3018]
R5F2L388ADFA@QFP80(single wire) [DX3018]
R5F2L388ADFP@QFP80 [DX3016]
R5F2L388ADFP@QFP80(single wire) [DX3016]
R5F2L388ANFA@QFP80 [DX3018]
R5F2L388ANFA@QFP80(single wire) [DX3018]
R5F2L388ANFP@QFP80 [DX3016]
R5F2L388ANFP@QFP80(single wire) [DX3016]
R5F2L388BDFA@QFP80 [DX3018]
R5F2L388BDFA@QFP80(single wire) [DX3018]
R5F2L388BDFP@QFP80 [DX3016]
R5F2L388BDFP@QFP80(single wire) [DX3016]
R5F2L388BNFA@QFP80 [DX3018]
R5F2L388BNFA@QFP80(single wire) [DX3018]
R5F2L388BNFP@QFP80 [DX3016]
R5F2L388BNFP@QFP80(single wire) [DX3016]
R5F2L388CDFA@QFP80 [DX3018]
R5F2L388CDFA@QFP80(single wire) [DX3018]
R5F2L388CDFP@QFP80 [DX3016]
R5F2L388CDFP@QFP80(single wire) [DX3016]
R5F2L388CNFA@QFP80 [DX3018]
R5F2L388CNFA@QFP80(single wire) [DX3018]
R5F2L388CNFP@QFP80 [DX3016]
R5F2L388CNFP@QFP80(single wire) [DX3016]
R5F2L38AADFA@QFP80 [DX3018]
R5F2L38AADFA@QFP80(single wire) [DX3018]

R5F2L38AADFP@QFP80 [DX3016]
R5F2L38AADFP@QFP80(single wire) [DX3016]
R5F2L38AANFA@QFP80 [DX3018]
R5F2L38AANFA@QFP80(single wire) [DX3018]
R5F2L38AANFP@QFP80 [DX3016]
R5F2L38AANFP@QFP80(single wire) [DX3016]
R5F2L38ABDFA@QFP80 [DX3018]
R5F2L38ABDFA@QFP80(single wire) [DX3018]
R5F2L38ABDFP@QFP80 [DX3016]
R5F2L38ABDFP@QFP80(single wire) [DX3016]
R5F2L38ABNFA@QFP80 [DX3018]
R5F2L38ABNFA@QFP80(single wire) [DX3018]
R5F2L38ABNFP@QFP80 [DX3016]
R5F2L38ABNFP@QFP80(single wire) [DX3016]
R5F2L38ACDFA@QFP80 [DX3018]
R5F2L38ACDFA@QFP80(single wire) [DX3018]
R5F2L38ACDFP@QFP80 [DX3016]
R5F2L38ACDFP@QFP80(single wire) [DX3016]
R5F2L38ACNFA@QFP80 [DX3018]
R5F2L38ACNFA@QFP80(single wire) [DX3018]
R5F2L38ACNFP@QFP80 [DX3016]
R5F2L38ACNFP@QFP80(single wire) [DX3016]
R5F2L38CADFA@QFP80 [DX3018]
R5F2L38CADFA@QFP80(single wire) [DX3018]
R5F2L38CADFP@QFP80 [DX3016]
R5F2L38CADFP@QFP80(single wire) [DX3016]
R5F2L38CANFA@QFP80 [DX3018]
R5F2L38CANFA@QFP80(single wire) [DX3018]
R5F2L38CANFP@QFP80 [DX3016]
R5F2L38CANFP@QFP80(single wire) [DX3016]
R5F2L38CBDFA@QFP80 [DX3018]
R5F2L38CBDFA@QFP80(single wire) [DX3018]
R5F2L38CBDFP@QFP80 [DX3016]
R5F2L38CBDFP@QFP80(single wire) [DX3016]
R5F2L38CBNFA@QFP80 [DX3018]
R5F2L38CBNFA@QFP80(single wire) [DX3018]
R5F2L38CBNFP@QFP80 [DX3016]
R5F2L38CBNFP@QFP80(single wire) [DX3016]
R5F2L38CCDFA@QFP80 [DX3018]
R5F2L38CCDFA@QFP80(single wire) [DX3018]
R5F2L38CCDFP@QFP80 [DX3016]
R5F2L38CCDFP@QFP80(single wire) [DX3016]
R5F2L38CCNFA@QFP80 [DX3018]
R5F2L38CCNFA@QFP80(single wire) [DX3018]
R5F2L38CCNFP@QFP80 [DX3016]
R5F2L38CCNFP@QFP80(single wire) [DX3016]
R5F2L3A7ADFA@PQFP100 [DX3023]
R5F2L3A7ADFA@PQFP100(single) [DX3023]

R5F2L3A7ADFP@PQFP100 [DX3021]
R5F2L3A7ADFP@PQFP100(single) [DX3021]
R5F2L3A7ANFA@PQFP100 [DX3023]
R5F2L3A7ANFA@PQFP100(single) [DX3023]
R5F2L3A7ANFP@PQFP100 [DX3021]
R5F2L3A7ANFP@PQFP100(single) [DX3021]
R5F2L3A7BDFA@PQFP100 [DX3023]
R5F2L3A7BDFA@PQFP100(single) [DX3023]
R5F2L3A7BDFP@PQFP100 [DX3021]
R5F2L3A7BDFP@PQFP100(single) [DX3021]
R5F2L3A7BNFA@PQFP100 [DX3023]
R5F2L3A7BNFA@PQFP100(single) [DX3023]
R5F2L3A7BNFP@PQFP100 [DX3021]
R5F2L3A7BNFP@PQFP100(single) [DX3021]
R5F2L3A7CDFA@PQFP100 [DX3023]
R5F2L3A7CDFA@PQFP100(single) [DX3023]
R5F2L3A7CDFP@PQFP100 [DX3021]
R5F2L3A7CDFP@PQFP100(single) [DX3021]
R5F2L3A7CNFA@PQFP100 [DX3023]
R5F2L3A7CNFA@PQFP100(single) [DX3023]
R5F2L3A7CNFP@PQFP100 [DX3021]
R5F2L3A7CNFP@PQFP100(single) [DX3021]
R5F2L3A8ADFA@PQFP100 [DX3023]
R5F2L3A8ADFA@PQFP100(single) [DX3023]
R5F2L3A8ADFP@PQFP100 [DX3021]
R5F2L3A8ADFP@PQFP100(single) [DX3021]
R5F2L3A8ANFA@PQFP100 [DX3023]
R5F2L3A8ANFA@PQFP100(single) [DX3023]
R5F2L3A8ANFP@PQFP100 [DX3021]
R5F2L3A8ANFP@PQFP100(single) [DX3021]
R5F2L3A8BDFA@PQFP100 [DX3023]
R5F2L3A8BDFA@PQFP100(single) [DX3023]
R5F2L3A8BDFP@PQFP100 [DX3021]
R5F2L3A8BDFP@PQFP100(single) [DX3021]
R5F2L3A8BNFA@PQFP100 [DX3023]
R5F2L3A8BNFA@PQFP100(single) [DX3023]
R5F2L3A8BNFP@PQFP100 [DX3021]
R5F2L3A8BNFP@PQFP100(single) [DX3021]
R5F2L3A8CDFA@PQFP100 [DX3023]
R5F2L3A8CDFA@PQFP100(single) [DX3023]
R5F2L3A8CDFP@PQFP100 [DX3021]
R5F2L3A8CDFP@PQFP100(single) [DX3021]
R5F2L3A8CNFA@PQFP100 [DX3023]
R5F2L3A8CNFA@PQFP100(single) [DX3023]
R5F2L3A8CNFP@PQFP100 [DX3021]
R5F2L3A8CNFP@PQFP100(single) [DX3021]
R5F2L3AAADFA@PQFP100 [DX3023]
R5F2L3AAADFA@PQFP100(single) [DX3023]

R5F2L3AAADFP@PQFP100 [DX3021]
R5F2L3AAADFP@PQFP100(single) [DX3021]
R5F2L3AAANFA@PQFP100 [DX3023]
R5F2L3AAANFA@PQFP100(single) [DX3023]
R5F2L3AAANFP@PQFP100 [DX3021]
R5F2L3AAANFP@PQFP100(single) [DX3021]
R5F2L3AABDFA@PQFP100 [DX3023]
R5F2L3AABDFA@PQFP100(single) [DX3023]
R5F2L3AABDFP@PQFP100 [DX3021]
R5F2L3AABDFP@PQFP100(single) [DX3021]
R5F2L3AABNFA@PQFP100 [DX3023]
R5F2L3AABNFA@PQFP100(single) [DX3023]
R5F2L3AABNFP@PQFP100 [DX3021]
R5F2L3AABNFP@PQFP100(single) [DX3021]
R5F2L3AACDFA@PQFP100 [DX3023]
R5F2L3AACDFA@PQFP100(single) [DX3023]
R5F2L3AACDFP@PQFP100 [DX3021]
R5F2L3AACDFP@PQFP100(single) [DX3021]
R5F2L3AACNFA@PQFP100 [DX3023]
R5F2L3AACNFA@PQFP100(single) [DX3023]
R5F2L3AACNFP@PQFP100 [DX3021]
R5F2L3AACNFP@PQFP100(single) [DX3021]
R5F2L3ACADFA@PQFP100 [DX3023]
R5F2L3ACADFA@PQFP100(single) [DX3023]
R5F2L3ACADFP@PQFP100 [DX3021]
R5F2L3ACADFP@PQFP100(single) [DX3021]
R5F2L3ACANFA@PQFP100 [DX3023]
R5F2L3ACANFA@PQFP100(single) [DX3023]
R5F2L3ACANFP@PQFP100 [DX3021]
R5F2L3ACANFP@PQFP100(single) [DX3021]
R5F2L3ACBDFA@PQFP100 [DX3023]
R5F2L3ACBDFA@PQFP100(single) [DX3023]
R5F2L3ACBDFP@PQFP100 [DX3021]
R5F2L3ACBDFP@PQFP100(single) [DX3021]
R5F2L3ACBNFA@PQFP100 [DX3023]
R5F2L3ACBNFA@PQFP100(single) [DX3023]
R5F2L3ACBNFP@PQFP100 [DX3021]
R5F2L3ACBNFP@PQFP100(single) [DX3021]
R5F2L3ACCDFA@PQFP100 [DX3023]
R5F2L3ACCDFA@PQFP100(single) [DX3023]
R5F2L3ACCDFP@PQFP100 [DX3021]
R5F2L3ACCDFP@PQFP100(single) [DX3021]
R5F2L3ACCNFA@PQFP100 [DX3023]
R5F2L3ACCNFA@PQFP100(single) [DX3023]
R5F2L3ACCNFP@PQFP100 [DX3021]
R5F2L3ACCNFP@PQFP100(single) [DX3021]
R5F2M110ADDD(single) [DX0001]
R5F2M110ADSP@TSSOP14(single) [DX1000]

R5F2M110ANDD(single) [DX0001]
R5F2M110ANSP@TSSOP14(single) [DX1000]
R5F2M111ADDD(single) [DX0001]
R5F2M111ADSP@TSSOP14(single) [DX1000]
R5F2M111ANDD(single) [DX0001]
R5F2M111ANSP@TSSOP14(single) [DX1000]
R5F2M112ADDD(single) [DX0001]
R5F2M112ADSP@TSSOP14(single) [DX1000]
R5F2M112ANDD(single) [DX0001]
R5F2M112ANSP@TSSOP14(single) [DX1000]
R5F2M120ADDD(single) [DX0001]
R5F2M120ADSP@TSSOP20(single) [DX1000]
R5F2M120ANDD(single) [DX0001]
R5F2M120ANSP@TSSOP20(single) [DX1000]
R5F2M121ADDD(single) [DX0001]
R5F2M121ADSP@TSSOP20(single) [DX1000]
R5F2M121ANDD(single) [DX0001]
R5F2M121ANSP@TSSOP20(single) [DX1000]
R5F2M122ADDD(single) [DX0001]
R5F2M122ADSP@TSSOP20(single) [DX1000]
R5F2M122ANDD(single) [DX0001]
R5F2M122ANSP@TSSOP20(single) [DX1000]
R5F35623JFE [DX3016]
R5F35623KFE [DX3016]
R5F35626JFE [DX3016]
R5F35626KFE [DX3016]
R5F3562EJFE [DX3016]
R5F3562EKFE [DX3016]
R5F35630JFF [DX3011]
R5F35630KFF [DX3011]
R5F35633JFF [DX3011]
R5F35633KFF [DX3011]
R5F35636JFF [DX3011]
R5F35636KFF [DX3011]
R5F3563EJFF [DX3011]
R5F3563EKFF [DX3011]
R5F35L23JFE [DX3016]
R5F35L23KFE [DX3016]
R5F35L26JFE [DX3016]
R5F35L26KFE [DX3016]
R5F35L2EJFE [DX3016]
R5F35L2EKFE [DX3016]
R5F35L30JFF [DX3011]
R5F35L30KFF [DX3011]
R5F35L33JFF [DX3011]
R5F35L33KFF [DX3011]
R5F35L36JFF [DX3011]
R5F35L36KFF [DX3011]
R5F35L3EJFF [DX3011]
R5F35L3EKFF [DX3011]
R5F363A6DFA@PQFP100 [DX3045]
R5F363A6DFB@QFP100 [DX3021]
R5F363A6NFA@PQFP100 [DX3045]
R5F363A6NFB@QFP100 [DX3021]
R5F363AEDFA@PQFP100 [DX3045]
R5F363AEDFB@QFP100 [DX3021]
R5F363AENFA@PQFP100 [DX3045]
R5F363AENFB@QFP100 [DX3021]
R5F363AKDFA@PQFP100 [DX3045]
R5F363AKDFB@QFP100 [DX3021]
R5F363AKNFA@PQFP100 [DX3045]
R5F363AKNFB@QFP100 [DX3021]
R5F363AMDFA@PQFP100 [DX3045]
R5F363AMDFB@QFP100 [DX3021]
R5F363AMNFA@PQFP100 [DX3045]
R5F363AMNFB@QFP100 [DX3021]
R5F36406DFA@PQFP100 [DX3045]
R5F36406DFB@QFP100 [DX3021]
R5F36406NFA@PQFP100 [DX3045]
R5F36406NFB@QFP100 [DX3021]
R5F3640DDFA@PQFP100 [DX3045]
R5F3640DDFB@QFP100 [DX3021]
R5F3640DNFA@PQFP100 [DX3045]
R5F3640DNFB@QFP100 [DX3021]

R5F3640MDFA@PQFP100 [DX3045]
R5F3640MDFB@QFP100 [DX3021]
R5F3640MNFA@PQFP100 [DX3045]
R5F3640MNFB@QFP100 [DX3021]
R5F364A6DFA@PQFP100 [DX3045]
R5F364A6DFB@QFP100 [DX3021]
R5F364A6NFA@PQFP100 [DX3045]
R5F364A6NFB@QFP100 [DX3021]
R5F364AEDFA@PQFP100 [DX3045]
R5F364AEDFB@QFP100 [DX3021]
R5F364AENFA@PQFP100 [DX3045]
R5F364AENFB@QFP100 [DX3021]
R5F364AMDFA@PQFP100 [DX3045]
R5F364AMDFB@QFP100 [DX3021]
R5F364AMNFA@PQFP100 [DX3045]
R5F364AMNFB@QFP100 [DX3021]
R5F36506DFA@PQFP100 [DX3045]
R5F36506DFB@QFP100 [DX3021]
R5F36506EFB@QFP100 [DX3021]
R5F36506KFB@QFP100 [DX3021]
R5F36506MFB@QFP100 [DX3021]
R5F36506NFA@PQFP100 [DX3045]
R5F36506NFB@QFP100 [DX3021]
R5F36506RFB@QFP100 [DX3021]
R5F36506TFB@QFP100 [DX3021]
R5F3650EDFA@PQFP100 [DX3045]
R5F3650EDFB@QFP100 [DX3021]
R5F3650ENFA@PQFP100 [DX3045]
R5F3650KDFA@PQFP100 [DX3045]
R5F3650KDFB@QFP100 [DX3021]
R5F3650KNFA@PQFP100 [DX3045]
R5F3650MDFA@PQFP100 [DX3045]
R5F3650MDFB@QFP100 [DX3021]
R5F3650MNFA@PQFP100 [DX3045]
R5F3650NDFA@PQFP100 [DX3045]
R5F3650NDFB@QFP100 [DX3021]
R5F3650NNFA@PQFP100 [DX3045]
R5F3650NNFB@QFP100 [DX3021]
R5F3650RDFA@PQFP100 [DX3045]
R5F3650RDFB@QFP100 [DX3021]
R5F3650RNFA@PQFP100 [DX3045]
R5F3650TDFA@PQFP100 [DX3045]
R5F3650TDFB@QFP100 [DX3021]
R5F3650TNFA@PQFP100 [DX3045]
R5F3651EDFC@PQFP128 [DX3032]
R5F3651ENFC@PQFP128 [DX3032]
R5F3651KDFC@PQFP128 [DX3032]
R5F3651KNFC@PQFP128 [DX3032]
R5F3651MDFC@PQFP128 [DX3032]
R5F3651MNFC@PQFP128 [DX3032]
R5F3651NDFC@PQFP128 [DX3032]
R5F3651NNFC@PQFP128 [DX3032]
R5F3651RDFC@PQFP128 [DX3032]
R5F3651RNFC@PQFP128 [DX3032]
R5F3651TDFC@PQFP128 [DX3032]
R5F3651TNFC@PQFP128 [DX3032]
R5F36CA6DFA [DX3045]
R5F36CA6DFB [DX3021]
R5F36CA6NFA [DX3045]
R5F36CA6NFB [DX3021]
R5F36CAEDFA [DX3045]
R5F36CAEDFB [DX3021]
R5F36CAENFA [DX3045]
R5F36CAENFB [DX3021]
R5F36CAKDFA [DX3045]
R5F36CAKDFB [DX3021]
R5F36CAKNFA [DX3045]
R5F36CAKNFB [DX3021]
R5F36CAMDFA [DX3045]
R5F36CAMDFB [DX3021]
R5F36CAMNFA [DX3045]
R5F36CAMNFB [DX3021]
R5F51111ADFL@QFP48(Uart) [DX3007]
R5F52106ADFM@QFP64(Uart) [DX3011]
R5F52106ADFP@QFP100(Uart) [DX3021]
R5F52106BDFM@QFP64(Uart) [DX3011]
R5F52106BDFP@QFP100(Uart) [DX3021]
R5F56216BDFB@QFP144 [DX3051]
R5F56216BDFP@QFP100 [DX3043]
R5F56217BDFB@QFP144 [DX3051]
R5F56217BDFP@QFP100 [DX3043]
R5F56218BDFB@QFP144 [DX3051]
R5F56218BDFP@QFP100 [DX3043]
R5F562N7ADFB@QFP144 [DX3051]
R5F562N7ADFP@QFP100 [DX3043]
R5F562N7BDFB@QFP144 [DX3051]
R5F562N7BDFP@QFP100 [DX3043]
R5F562N8ADFB@QFP144 [DX3051]
R5F562N8ADFP@QFP100 [DX3043]
R5F562N8BDFB@QFP144 [DX3051]
R5F562N8BDFP@QFP100 [DX3043]

R5F562T6ADFF@QFP80 [DX3017]
R5F562T6ADFF@QFP80(serial) [DX3017]
R5F562T6ADFK@QFP64(serial) [DX3013]
R5F562T6ADFM@QFP64(serial) [DX3011]
R5F562T6BDFF@QFP80 [DX3017]
R5F562T6BDFF@QFP80(serial) [DX3017]
R5F562T6BDFK@QFP64(serial) [DX3013]
R5F562T6BDFM@QFP64(serial) [DX3011]
R5F562T6DDFF@QFP80 [DX3017]
R5F562T6DDFF@QFP80(serial) [DX3017]
R5F562T6DDFK@QFP64(serial) [DX3013]
R5F562T6DDFM@QFP64(serial) [DX3011]
R5F562T6EDFF@QFP80 [DX3017]
R5F562T6EDFF@QFP80(serial) [DX3017]
R5F562T6EDFK@QFP64(serial) [DX3013]
R5F562T6EDFM@QFP64(serial) [DX3011]
R5F562T7ADFF [DX3017]
R5F562T7ADFF@QFP80(serial) [DX3017]
R5F562T7ADFH [DX3026]
R5F562T7ADFH@QFP112(serial) [DX3026]
R5F562T7ADFK@QFP64(serial) [DX3013]
R5F562T7ADFM@QFP64(serial) [DX3011]
R5F562T7ADFP [DX3043]
R5F562T7ADFP@QFP100(serial) [DX3043]
R5F562T7BDFF [DX3017]
R5F562T7BDFF@QFP80(serial) [DX3017]
R5F562T7BDFH [DX3026]
R5F562T7BDFH@QFP112(serial) [DX3026]
R5F562T7BDFK@QFP64(serial) [DX3013]
R5F562T7BDFM@QFP64(serial) [DX3011]
R5F562T7BDFP [DX3043]
R5F562T7BDFP@QFP100(serial) [DX3043]
R5F562T7DDFF [DX3017]
R5F562T7DDFF@QFP80(serial) [DX3017]
R5F562T7DDFH [DX3026]
R5F562T7DDFH@QFP112(serial) [DX3026]
R5F562T7DDFK@QFP64(serial) [DX3013]
R5F562T7DDFM@QFP64(serial) [DX3011]
R5F562T7DDFP [DX3043]
R5F562T7DDFP@QFP100(serial) [DX3043]
R5F562T7EDFF [DX3017]
R5F562T7EDFF@QFP80(serial) [DX3017]
R5F562T7EDFH [DX3026]
R5F562T7EDFH@QFP112(serial) [DX3026]
R5F562T7EDFK@QFP64(serial) [DX3013]
R5F562T7EDFM@QFP64(serial) [DX3011]
R5F562T7EDFP [DX3043]
R5F562T7EDFP@QFP100(serial) [DX3043]

R5F562TAADFF [DX3017]
R5F562TAADFF@QFP80(serial) [DX3017]
R5F562TAADFH [DX3026]
R5F562TAADFH@QFP112(serial) [DX3026]
R5F562TAADFK@QFP64(serial) [DX3013]
R5F562TAADFM@QFP64(serial) [DX3011]
R5F562TAADFP [DX3043]
R5F562TAADFP@QFP100(serial) [DX3043]
R5F562TABDFF [DX3017]
R5F562TABDFF@QFP80(serial) [DX3017]
R5F562TABDFH [DX3026]
R5F562TABDFH@QFP112(serial) [DX3026]
R5F562TABDFK@QFP64(serial) [DX3013]
R5F562TABDFM@QFP64(serial) [DX3011]
R5F562TABDFP [DX3043]
R5F562TABDFP@QFP100(serial) [DX3043]
R5F562TADDFF [DX3017]
R5F562TADDFF@QFP80(serial) [DX3017]
R5F562TADDFH [DX3026]
R5F562TADDFH@QFP112(serial) [DX3026]
R5F562TADDFK@QFP64(serial) [DX3013]
R5F562TADDFM@QFP64(serial) [DX3011]
R5F562TADDFP [DX3043]
R5F562TADDFP@QFP100(serial) [DX3043]
R5F562TAEDFF [DX3017]
R5F562TAEDFF@QFP80(serial) [DX3017]
R5F562TAEDFH [DX3026]
R5F562TAEDFH@QFP112(serial) [DX3026]
R5F562TAEDFK@QFP64(serial) [DX3013]
R5F562TAEDFM@QFP64(serial) [DX3011]
R5F562TAEDFP [DX3043]
R5F562TAEDFP@QFP100(serial) [DX3043]
R5F61523FP@QFP100 [DX3043]
R5F61524FP@QFP100 [DX3043]
R5F61525FP@QFP100 [DX3043]
R5F61527FP@QFP100 [DX3043]
R5F61632FPV@QFP120 [DX3027]
R5F61632LFPV@QFP120 [DX3027]
R5F61634FPV@QFP120 [DX3027]
R5F61634LFPV@QFP120 [DX3027]
R5F61638FPV@QFP120 [DX3027]
R5F61638LFPV@QFP120 [DX3027]
R5F61641FPV@QFP144 [DX3035]
R5F61641LFPV@QFP144 [DX3035]
R5F61642AFPV@QFP144 [DX3035]
R5F61642FPV@QFP144 [DX3035]
R5F61642LFPV@QFP144 [DX3035]
R5F61643FPV@QFP144 [DX3035]
R5F61643LFPV@QFP144 [DX3035]
R5F61644AFPV@QFP144 [DX3035]
R5F61644FPV@QFP144 [DX3035]
R5F61644LFPV@QFP144 [DX3035]
R5F61645FPV@QFP144 [DX3035]
R5F61645LFPV@QFP144 [DX3035]
R5F61648AFPV@QFP144 [DX3035]
R5F61648FPV@QFP144 [DX3035]
R5F61648LFPV@QFP144 [DX3035]
R5F61652FPV@QFP120 [DX3027]
R5F61652MFPV@QFP120 [DX3027]
R5F61653MFPV@QFP120 [DX3027]
R5F61653RFPV@QFP120 [DX3027]
R5F61654MFPV@QFP120 [DX3027]
R5F61654RFPV@QFP120 [DX3027]
R5F61655FPV@QFP120 [DX3027]

R5F61655MFPV@QFP120 [DX3027]
R5F61658MFPV@QFP120 [DX3027]
R5F61658RFPV@QFP120 [DX3027]
R5F61663MFPV@QFP144 [DX3035]
R5F61663RFPV@QFP144 [DX3035]
R5F61664MFPV@QFP144 [DX3035]
R5F61664RFPV@QFP144 [DX3035]
R5F61668MFPV@QFP144 [DX3035]
R5F61668RFPV@QFP144 [DX3035]
R5F61725FPV@QFP100 [DX3043]
R5F61725SFPV@QFP100 [DX3043]
R5F61726SFPV@QFP100 [DX3043]
R5F61727SFPV@QFP100 [DX3043]
R5F64110DFB@TQFP100 [DX3021]
R5F64110NFB@TQFP100 [DX3021]
R5F64111DFB@TQFP100 [DX3021]
R5F64111NFB@TQFP100 [DX3021]
R5F64112DFB@TQFP100 [DX3021]
R5F64112NFB@TQFP100 [DX3021]
R5F64114DFB@TQFP100 [DX3021]
R5F64114NFB@TQFP100 [DX3021]
R5F64115DFB@TQFP100 [DX3021]
R5F64115NFB@TQFP100 [DX3021]
R5F64116DFB@TQFP100 [DX3021]
R5F64116NFB@TQFP100 [DX3021]
R5F6416JADFD [DX3035]
R5F6416JANFD [DX3035]
R5F6416JAPFD [DX3035]
R5F6416KADFD [DX3035]
R5F6416KANFD [DX3035]
R5F6416KAPFD [DX3035]
R5F6416LADFD [DX3035]
R5F6416LANFD [DX3035]
R5F6416LAPFD [DX3035]
R5F6416MADFD [DX3035]
R5F6416MANFD [DX3035]
R5F6416MAPFD [DX3035]
R5F64175DFB [DX3021]
R5F64175DFD [DX3035]
R5F64175NFB [DX3021]
R5F64175NFD [DX3035]
R5F64175PFB [DX3021]
R5F64175PFD [DX3035]
R5F64176DFB [DX3021]
R5F64176DFD [DX3035]
R5F64176NFB [DX3021]
R5F64176NFD [DX3035]
R5F64176PFB [DX3021]
R5F64176PFD [DX3035]
R5F64177DFB [DX3021]
R5F64177DFD [DX3035]
R5F64177NFB [DX3021]
R5F64177NFD [DX3035]
R5F64177PFB [DX3021]
R5F64177PFD [DX3035]
R5F64178DFB [DX3021]
R5F64178DFD [DX3035]
R5F64178NFB [DX3021]
R5F64178NFD [DX3035]
R5F64178PFB [DX3021]
R5F64178PFD [DX3035]
R5F64179DFB [DX3021]
R5F64179DFD [DX3035]
R5F64179NFB [DX3021]
R5F64179NFD [DX3035]
R5F64179PFB [DX3021]
R5F64179PFD [DX3035]
R5F64185DFB [DX3021]
R5F64185DFD [DX3035]
R5F64185HDFB [DX3021]
R5F64185HDFD [DX3035]
R5F64185HNFB [DX3021]
R5F64185HNFD [DX3035]
R5F64185HPFB [DX3021]
R5F64185HPFD [DX3035]
R5F64185NFB [DX3021]
R5F64185NFD [DX3035]
R5F64185PFB [DX3021]
R5F64185PFD [DX3035]
R5F64186DFB [DX3021]
R5F64186DFD [DX3035]
R5F64186HDFB [DX3021]
R5F64186HDFD [DX3035]
R5F64186HNFB [DX3021]
R5F64186HNFD [DX3035]
R5F64186HPFB [DX3021]
R5F64186HPFD [DX3035]
R5F64186NFB [DX3021]
R5F64186NFD [DX3035]
R5F64186PFB [DX3021]
R5F64186PFD [DX3035]
R5F64187DFB [DX3021]
R5F64187DFD [DX3035]
R5F64187HDFB [DX3021]
R5F64187HDFD [DX3035]
R5F64187HNFB [DX3021]

R5F64187HNFD [DX3035]
R5F64187HPFD [DX3035]
R5F64187NFD [DX3035]
R5F64187PFD [DX3035]
R5F64188DFD [DX3035]
R5F64188HDFD [DX3035]
R5F64188HNFD [DX3035]
R5F64188HPFD [DX3035]
R5F64188NFD [DX3035]
R5F64188PFD [DX3035]
R5F64189DFD [DX3035]
R5F64189HDFD [DX3035]
R5F64189HNFD [DX3035]
R5F64189HPFD [DX3035]
R5F64189NFD [DX3035]
R5F64189PFD [DX3035]
R5F64600KFP@QFP80 [DX3016]
R5F64601JFP@QFP80 [DX3016]
R5F64601LFP@QFP80 [DX3016]
R5F6460EKFP@QFP80 [DX3016]
R5F6460FJFP@QFP80 [DX3016]
R5F6460FLFP@QFP80 [DX3016]
R5F64610KFP@QFP80 [DX3016]
R5F64611JFP@QFP80 [DX3016]
R5F64611LFP@QFP80 [DX3016]
R5F6461EKFP@QFP80 [DX3016]
R5F6461FJFP@QFP80 [DX3016]
R5F6461FLFP@QFP80 [DX3016]
R5F646Z0KFP@QFP80 [DX3016]
R5F646Z1JFP@QFP80 [DX3016]
R5F646Z1LFP@QFP80 [DX3016]
R5F646ZEKFP@QFP80 [DX3016]
R5F646ZFJFP@QFP80 [DX3016]
R5F646ZFLFP@QFP80 [DX3016]
R5F70834AD80FTV@QFP100 [DX3043]
R5F70834AN80FTV@QFP100 [DX3043]
R5F70835AN80FTV@QFP100 [DX3043]
R5F70844AN80FPV@QFP112 [DX3026]
R5F70845AN80FPV@QFP112 [DX3026]
R5F70854AN80FPV@TQFP144 [DX3035]
R5F70855AN80FPV@TQFP144 [DX3035]
R5F70865AN80FPV@QFP176 [DX3080]
R5F71242FPV@QFP48(serial) [DX3008]
R5F71243FPV@QFP48(serial) [DX3008]
R5F71252FAV@QFP64(serial) [DX3014]
R5F71252FPV@QFP64(serial) [DX3011]
R5F71253FAV@QFP64(serial) [DX3014]
R5F71253FPV@QFP64(serial) [DX3011]
R5F64187HPFB [DX3021]
R5F64187NFB [DX3021]
R5F64187PFB [DX3021]
R5F64188DFB [DX3021]
R5F64188HDFB [DX3021]
R5F64188HNFB [DX3021]
R5F64188HPFB [DX3021]
R5F64188NFB [DX3021]
R5F64188PFB [DX3021]
R5F64189DFB [DX3021]
R5F64189HDFB [DX3021]
R5F64189HNFB [DX3021]
R5F64189HPFB [DX3021]
R5F64189NFB [DX3021]
R5F64189PFB [DX3021]
R5F64600JFP@QFP80 [DX3016]
R5F64600LFP@QFP80 [DX3016]
R5F64601KFP@QFP80 [DX3016]
R5F6460EJFP@QFP80 [DX3016]
R5F6460ELFP@QFP80 [DX3016]
R5F6460FKFP@QFP80 [DX3016]
R5F64610JFP@QFP80 [DX3016]
R5F64610LFP@QFP80 [DX3016]
R5F64611KFP@QFP80 [DX3016]
R5F6461EJFP@QFP80 [DX3016]
R5F6461ELFP@QFP80 [DX3016]
R5F6461FKFP@QFP80 [DX3016]
R5F646Z0JFP@QFP80 [DX3016]
R5F646Z0LFP@QFP80 [DX3016]
R5F646Z1KFP@QFP80 [DX3016]
R5F646ZEJFP@QFP80 [DX3016]
R5F646ZELFP@QFP80 [DX3016]
R5F646ZFKFP@QFP80 [DX3016]
R5F70834AD80BGV [DX5058]
R5F70834AN80BGV [DX5058]
R5F70835AD80FTV@QFP100 [DX3043]
R5F70844AD80FPV@QFP112 [DX3026]
R5F70845AD80FPV@QFP112 [DX3026]
R5F70854AD80FPV@TQFP144 [DX3035]
R5F70855AD80FPV@TQFP144 [DX3035]
R5F70865AD80FPV@QFP176 [DX3080]

R5F71374AD80FPV [DX3043]
R5F71374AN80FPV [DX3043]
R5F71424AK64FPV [DX3043]
R5F71424BJ80FPV [DX3043]
R5F71426AK64FPV [DX3043]
R5F71426BD80FPV [DX3043]
R5F71426BJ80FPV [DX3043]
R5F71464FPV@QFP80 [DX3017]
R5F71464FPV@QFP80(serial) [DX3017]
R5F71474AK64FPV [DX3043]
R5F71474BD80FPV [DX3043]
R5F71474BJ80FPV [DX3043]
R5F71475AK64FPV [DX3043]
R5F71475BD80FPV [DX3043]
R5F71475BJ80FPV [DX3043]
R5F71476AK64FPV [DX3043]
R5F71476BD80FPV [DX3043]
R5F71476BJ80FPV [DX3043]
R5F71494FPV@QFP100 [DX3021]
R5F72114FPV@QFP144 [DX3035]
R5F72115FPV@QFP144 [DX3035]
R5F72145ADFA@QFP176 [DX3089]
R5F72145ADFP@QFP176 [DX3111]
R5F72145BDFA@QFP176 [DX3089]
R5F72145BDFP@QFP176 [DX3111]
R5F72145GDFA@QFP176 [DX3089]
R5F72145GDFP@QFP176 [DX3111]
R5F72145HDFA@QFP176 [DX3089]
R5F72145HDFP@QFP176 [DX3111]
R5F72146ADFA@QFP176 [DX3089]
R5F72146ADFP@QFP176 [DX3111]
R5F72146BDFA@QFP176 [DX3089]
R5F72146BDFP@QFP176 [DX3111]
R5F72146GDFA@QFP176 [DX3089]
R5F72146GDFP@QFP176 [DX3111]
R5F72146HDFA@QFP176 [DX3089]
R5F72146HDFP@QFP176 [DX3111]
R5F72147ADFA@QFP176 [DX3089]
R5F72147ADFP@QFP176 [DX3111]
R5F72147BDFA@QFP176 [DX3089]
R5F72147BDFP@QFP176 [DX3111]
R5F72147GDFA@QFP176 [DX3089]
R5F72147GDFP@QFP176 [DX3111]
R5F72147HDFA@QFP176 [DX3089]
R5F72147HDFP@QFP176 [DX3111]
R5F72165ADFA@QFP176 [DX3089]
R5F72165ADFP@QFP176 [DX3111]
R5F72165BDFA@QFP176 [DX3089]
R5F72165BDFP@QFP176 [DX3111]
R5F72165GDFA@QFP176 [DX3089]
R5F72165GDFP@QFP176 [DX3111]
R5F72165HDFA@QFP176 [DX3089]
R5F72165HDFP@QFP176 [DX3111]
R5F72166ADFA@QFP176 [DX3089]
R5F72166ADFP@QFP176 [DX3111]
R5F72166BDFA@QFP176 [DX3089]
R5F72166BDFP@QFP176 [DX3111]
R5F72166GDFA@QFP176 [DX3089]
R5F72166GDFP@QFP176 [DX3111]
R5F72166HDFA@QFP176 [DX3089]
R5F72166HDFP@QFP176 [DX3111]
R5F72167ADFA@QFP176 [DX3089]
R5F72167ADFP@QFP176 [DX3111]
R5F72167BDFA@QFP176 [DX3089]
R5F72167BDFP@QFP176 [DX3111]
R5F72167GDFA@QFP176 [DX3089]
R5F72167GDFP@QFP176 [DX3111]
R5F72167HDFA@QFP176 [DX3089]
R5F72167HDFP@QFP176 [DX3111]
R5F72865DFP [DX3114]
R5F72865NFP [DX3114]
R5F72866DFP [DX3114]
R5F72866NFP [DX3114]
R5F72867DFP [DX3114]
R5F72867NFP [DX3114]
R5G0C302FA@QFP32 [DX3001]
R5G0C314D@SDIP32 [DX0032]
R5G0C328FA@QFP32 [DX3001]
R5G0C514FA [DX3013]
R5G0C514FP@QFP80 [DX3020]
R5R0C028FA@QFP32 [DX3010]
R5R0C0B4SP@TSSOP24(single wire) [DX1012]
R7F01592ESN [DX1033]
R7F01692ESN [DX1033]
R7F0C001G2DFB [DX3007]
R7F0C001L2DFB [DX3011]
R7F0C002G2DFB [DX3007]
R7F0C002L2DFB [DX3011]
R7F0C003M2DFB [DX3016]
R7F0C004M2DFB [DX3016]
R7F0C008A2DSP [DX1026]
R7F0C008B2DFP [DX3001]
R7F0C008F2DFP [DX3005]
R7F0C009A2DSP [DX1026]

R7F0C009B2DFP [DX3001]
R7F0C009F2DFP [DX3005]
R7F0C011B2001DFP [DX3001]
R7F0C012B2001DFP [DX3001]
R7F0C013B2001DFP [DX3001]
R7F0C014 [DX3001]
R7F0C019L2DFB [DX3011]
R7F0C903 [DX3001]
R7F0C904 [DX3001]
R7F0C905 [DX3001]
R7F0C906 [DX3001]
R7F0C907 [DX3001]
R7F0C908 [DX3001]
uPD70F3114GC [DX3021]
uPD70F3114GK [DX3023]
uPD70F3116GC [DX3021]
uPD70F3116GK [DX3023]
UPD70F3329GC [DX3014]
uPD70F3333GC [DX3043]
uPD70F3333GCA [DX3043]
uPD70F3334GC [DX3043]
uPD70F3334GCA [DX3043]
uPD70F3335GC [DX3043]
uPD70F3335GCA [DX3043]
uPD70F3336GC [DX3043]
uPD70F3336GCA [DX3043]
uPD70F3340GC [DX3043]
uPD70F3340GCA [DX3043]
uPD70F3340GJ@LQFP144 [DX3051]
uPD70F3340GJ@LQFP144(Uart) [DX3051]
uPD70F3340GJA@LQFP144 [DX3051]
uPD70F3340GJA@LQFP144(Uart) [DX3051]
uPD70F3341GC [DX3043]
uPD70F3341GCA [DX3043]
uPD70F3341GJ@LQFP144 [DX3051]
uPD70F3341GJ@LQFP144(Uart) [DX3051]
uPD70F3341GJA@LQFP144 [DX3051]
uPD70F3341GJA@LQFP144(Uart) [DX3051]
uPD70F3342GC [DX3043]
uPD70F3342GCA [DX3043]
uPD70F3342GJ@LQFP144 [DX3051]
uPD70F3342GJ@LQFP144(Uart) [DX3051]
uPD70F3342GJA@LQFP144 [DX3051]
uPD70F3342GJA@LQFP144(Uart) [DX3051]
uPD70F3343GC [DX3043]
uPD70F3343GCA [DX3043]
uPD70F3343GJ@LQFP144 [DX3051]
uPD70F3343GJ@LQFP144(Uart) [DX3051]
uPD70F3343GJA@LQFP144 [DX3051]
uPD70F3343GJA@LQFP144(Uart) [DX3051]
uPD70F3344GJ@LQFP144 [DX3051]
uPD70F3344GJ@LQFP144(Uart) [DX3051]
uPD70F3344GJA@LQFP144 [DX3051]
uPD70F3344GJA@LQFP144(Uart) [DX3051]
uPD70F3345GJ@LQFP144 [DX3051]
uPD70F3345GJ@LQFP144(Uart) [DX3051]
uPD70F3345GJA@LQFP144 [DX3051]
uPD70F3345GJA@LQFP144(Uart) [DX3051]
uPD70F3346GJ@LQFP144 [DX3051]
uPD70F3346GJ@LQFP144(Uart) [DX3051]
uPD70F3346GJA@LQFP144 [DX3051]
uPD70F3346GJA@LQFP144(Uart) [DX3051]
uPD70F3347GJ@LQFP144 [DX3051]
uPD70F3347GJ@LQFP144(Uart) [DX3051]
uPD70F3347GJA@LQFP144 [DX3051]

uPD70F3347GJA@LQFP144(Uart) [DX3051]
uPD70F3348GJ@LQFP144 [DX3051]
uPD70F3348GJ@LQFP144(Uart) [DX3051]
uPD70F3348GJA@LQFP144 [DX3051]
uPD70F3348GJA@LQFP144(Uart) [DX3051]
uPD70F3350GC [DX3043]　　uPD70F3350GCA [DX3043]
uPD70F3350GJ@LQFP144 [DX3051]
uPD70F3350GJ@LQFP144(Uart) [DX3051]
uPD70F3350GJA@LQFP144 [DX3051]
uPD70F3350GJA@LQFP144(Uart) [DX3051]
uPD70F3351GC [DX3043]　　uPD70F3351GCA [DX3043]
uPD70F3351GJ@LQFP144 [DX3051]
uPD70F3351GJ@LQFP144(Uart) [DX3051]
uPD70F3351GJA@LQFP144 [DX3051]
uPD70F3351GJA@LQFP144(Uart) [DX3051]
uPD70F3352GC [DX3043]　　uPD70F3352GCA [DX3043]
uPD70F3352GJ@LQFP144 [DX3051]
uPD70F3352GJ@LQFP144(Uart) [DX3051]
uPD70F3352GJA@LQFP144 [DX3051]
uPD70F3352GJA@LQFP144(Uart) [DX3051]
uPD70F3353GC [DX3043]　　uPD70F3353GCA [DX3043]
uPD70F3353GJ@LQFP144 [DX3051]
uPD70F3353GJ@LQFP144(Uart) [DX3051]
uPD70F3353GJA@LQFP144 [DX3051]
uPD70F3353GJA@LQFP144(Uart) [DX3051]
uPD70F3354GJ@LQFP144 [DX3051]
uPD70F3354GJ@LQFP144(Uart) [DX3051]
uPD70F3354GJA@LQFP144 [DX3051]
uPD70F3354GJA@LQFP144(Uart) [DX3051]
uPD70F3355GJ@LQFP144 [DX3051]
uPD70F3355GJ@LQFP144(Uart) [DX3051]
uPD70F3355GJA@LQFP144 [DX3051]
uPD70F3355GJA@LQFP144(Uart) [DX3051]
uPD70F3356GJ@LQFP144 [DX3051]
uPD70F3356GJ@LQFP144(Uart) [DX3051]
uPD70F3356GJA@LQFP144 [DX3051]
uPD70F3356GJA@LQFP144(Uart) [DX3051]
uPD70F3357GJ@LQFP144 [DX3051]
uPD70F3357GJ@LQFP144(Uart) [DX3051]
uPD70F3357GJA@LQFP144 [DX3051]
uPD70F3357GJA@LQFP144(Uart) [DX3051]
uPD70F3358GJ@LQFP144 [DX3051]
uPD70F3358GJ@LQFP144(Uart) [DX3051]
uPD70F3358GJA@LQFP144 [DX3051]
uPD70F3358GJA@LQFP144(Uart) [DX3051]
uPD70F3360GJ@LQFP144 [DX3051]
uPD70F3360GJ@LQFP144(Uart) [DX3051]
uPD70F3360GJA@LQFP144 [DX3051]

uPD70F3360GJA@LQFP144(Uart) [DX3051]
uPD70F3361GJ@LQFP144 [DX3051]
uPD70F3361GJ@LQFP144(Uart) [DX3051]
uPD70F3361GJA@LQFP144 [DX3051]
uPD70F3361GJA@LQFP144(Uart) [DX3051]
uPD70F3362GJ@LQFP144 [DX3051]
uPD70F3362GJ@LQFP144(Uart) [DX3051]
uPD70F3362GJA@LQFP144 [DX3051]
uPD70F3362GJA@LQFP144(Uart) [DX3051]
uPD70F3363GJ@LQFP144 [DX3051]
uPD70F3363GJ@LQFP144(Uart) [DX3051]
uPD70F3363GJA@LQFP144 [DX3051]
uPD70F3363GJA@LQFP144(Uart) [DX3051]
uPD70F3364GJ@LQFP144 [DX3051]
uPD70F3364GJ@LQFP144(Uart) [DX3051]
uPD70F3364GJA@LQFP144 [DX3051]
uPD70F3364GJA@LQFP144(Uart) [DX3051]
uPD70F3365GJ@LQFP144 [DX3051]
uPD70F3365GJ@LQFP144(Uart) [DX3051]
uPD70F3365GJA@LQFP144 [DX3051]
uPD70F3365GJA@LQFP144(Uart) [DX3051]
uPD70F3366GJ@LQFP144 [DX3051]
uPD70F3366GJ@LQFP144(Uart) [DX3051]
uPD70F3366GJA@LQFP144 [DX3051]
uPD70F3366GJA@LQFP144(Uart) [DX3051]
uPD70F3367GJ@LQFP144 [DX3051]
uPD70F3367GJ@LQFP144(Uart) [DX3051]
uPD70F3367GJA@LQFP144 [DX3051]
uPD70F3367GJA@LQFP144(Uart) [DX3051]
uPD70F3368GJ@LQFP144 [DX3051]
uPD70F3368GJ@LQFP144(Uart) [DX3051]
uPD70F3368GJA@LQFP144 [DX3051]
uPD70F3368GJA@LQFP144(Uart) [DX3051]

uPD70F3370 [DX3011]	uPD70F3371 [DX3011]
uPD70F3372 [DX3016]	uPD70F3373 [DX3016]
uPD70F3374 [DX3043]	uPD70F3375 [DX3043]
uPD70F3376 [DX3043]	uPD70F3377 [DX3043]
uPD70F3378 [DX3051]	uPD70F3379 [DX3051]
uPD70F3380 [DX3051]	uPD70F3381 [DX3051]
uPD70F3382 [DX3051]	uPD70F3383 [DX0001]
uPD70F3384 [DX0001]	uPD70F3385 [DX0001]
uPD70F3421AGJU [DX3051]	uPD70F3421GJU [DX3051]
uPD70F3422AGJU [DX3051]	uPD70F3422GJU [DX3051]
uPD70F3423AGJU [DX3051]	uPD70F3423GJU [DX3051]
uPD70F3424AGJU [DX3051]	uPD70F3424GJU [DX3051]
uPD70F3425AGJU [DX3051]	uPD70F3425GJU [DX3051]
uPD70F3426AGJU [DX3051]	uPD70F3426GJU [DX3051]
uPD70F3427AGDU [DX0001]	uPD70F3427GDU [DX0001]

uPD70F3451GC [DX3018]
uPD70F3452GC [DX3018]
uPD70F3453GC@LQFP100 [DX3043]
uPD70F3453GF@LQFP100 [DX3062]
uPD70F3454GC@LQFP100 [DX3043]
uPD70F3454GF@LQFP100 [DX3062]
uPD70F3455GC [DX3018]
uPD70F3456GC [DX3018]
uPD70F3610M1GAA [DX3085]
uPD70F3610M1GAA1 [DX3085]
uPD70F3610M1GAA2 [DX3085]
uPD70F3610M1GBA [DX3011]
uPD70F3610M1GBA1 [DX3011]
uPD70F3610M1GBA2 [DX3011]
uPD70F3610M2GAA [DX3085]
uPD70F3610M2GAA1 [DX3085]
uPD70F3610M2GAA2 [DX3085]
uPD70F3610M2GBA [DX3011]
uPD70F3610M2GBA1 [DX3011]
uPD70F3610M2GBA2 [DX3011]
uPD70F3611M1GAA [DX3085]
uPD70F3611M1GAA1 [DX3085]
uPD70F3611M1GAA2 [DX3085]
uPD70F3611M1GBA [DX3011]
uPD70F3611M1GBA1 [DX3011]
uPD70F3611M1GBA2 [DX3011]
uPD70F3611M2GAA [DX3085]
uPD70F3611M2GAA1 [DX3085]
uPD70F3611M2GAA2 [DX3085]
uPD70F3611M2GBA [DX3011]
uPD70F3611M2GBA1 [DX3011]
uPD70F3611M2GBA2 [DX3011]
uPD70F3612M1GAA [DX3085]
uPD70F3612M1GAA1 [DX3085]
uPD70F3612M1GAA2 [DX3085]
uPD70F3612M1GBA [DX3011]
uPD70F3612M1GBA1 [DX3011]
uPD70F3612M1GBA2 [DX3011]
uPD70F3612M2GAA [DX3085]
uPD70F3612M2GAA1 [DX3085]
uPD70F3612M2GAA2 [DX3085]
uPD70F3612M2GBA [DX3011]
uPD70F3612M2GBA1 [DX3011]
uPD70F3612M2GBA2 [DX3011]
uPD70F3613M1GAA [DX3085]
uPD70F3613M1GAA1 [DX3085]
uPD70F3613M1GAA2 [DX3085]
uPD70F3613M1GBA [DX3011]
uPD70F3613M1GBA1 [DX3011]
uPD70F3613M1GBA2 [DX3011]
uPD70F3613M2GAA [DX3085]
uPD70F3613M2GAA1 [DX3085]
uPD70F3613M2GAA2 [DX3085]
uPD70F3613M2GBA [DX3011]
uPD70F3613M2GBA1 [DX3011]
uPD70F3613M2GBA2 [DX3011]
uPD70F3614M1GAA [DX3085]
uPD70F3614M1GAA1 [DX3085]
uPD70F3614M1GAA2 [DX3085]
uPD70F3614M1GBA [DX3011]
uPD70F3614M1GBA1 [DX3011]
uPD70F3614M1GBA2 [DX3011]
uPD70F3614M2GAA [DX3085]
uPD70F3614M2GAA1 [DX3085]
uPD70F3614M2GAA2 [DX3085]
uPD70F3614M2GBA [DX3011]
uPD70F3614M2GBA1 [DX3011]
uPD70F3614M2GBA2 [DX3011]
uPD70F3615M1GBA [DX3016]
uPD70F3615M1GBA1 [DX3016]
uPD70F3615M1GBA2 [DX3016]
uPD70F3615M2GBA [DX3016]
uPD70F3615M2GBA1 [DX3016]
uPD70F3615M2GBA2 [DX3016]
uPD70F3616M1GBA [DX3016]
uPD70F3616M1GBA1 [DX3016]
uPD70F3616M1GBA2 [DX3016]
uPD70F3616M2GBA [DX3016]
uPD70F3616M2GBA1 [DX3016]
uPD70F3616M2GBA2 [DX3016]
uPD70F3617M1GBA [DX3016]
uPD70F3617M1GBA1 [DX3016]
uPD70F3617M1GBA2 [DX3016]
uPD70F3617M2GBA [DX3016]
uPD70F3617M2GBA1 [DX3016]
uPD70F3617M2GBA2 [DX3016]
uPD70F3618M1GBA [DX3016]
uPD70F3618M1GBA1 [DX3016]
uPD70F3618M1GBA2 [DX3016]
uPD70F3618M2GBA [DX3016]
uPD70F3618M2GBA1 [DX3016]
uPD70F3618M2GBA2 [DX3016]
uPD70F3619M1GBA [DX3016]
uPD70F3619M1GBA1 [DX3016]
uPD70F3619M1GBA2 [DX3016]
uPD70F3619M2GBA [DX3016]

uPD70F3619M2GBA1 [DX3016]
uPD70F3619M2GBA2 [DX3016]
uPD70F3620M1GBA [DX3043]
uPD70F3620M1GBA1 [DX3043]
uPD70F3620M1GBA2 [DX3043]
uPD70F3620M2GBA [DX3043]
uPD70F3620M2GBA1 [DX3043]
uPD70F3620M2GBA2 [DX3043]
uPD70F3621M1GBA [DX3043]
uPD70F3621M1GBA1 [DX3043]
uPD70F3621M1GBA2 [DX3043]
uPD70F3621M2GBA [DX3043]
uPD70F3621M2GBA1 [DX3043]
uPD70F3621M2GBA2 [DX3043]
uPD70F3622M1GBA [DX3043]
uPD70F3622M1GBA1 [DX3043]
uPD70F3622M1GBA2 [DX3043]
uPD70F3622M2GBA [DX3043]
uPD70F3622M2GBA1 [DX3043]
uPD70F3622M2GBA2 [DX3043]
uPD70F3623 [DX3011]
uPD70F3623(data flash) [DX3011]
uPD70F3623GK [DX3011]
uPD70F3623GK(data flash) [DX3011]
uPD70F3624 [DX3011]
uPD70F3624(data flash) [DX3011]
uPD70F3624GK [DX3011]
uPD70F3624GK(data flash) [DX3011]
uPD70F3625 [DX3016]
uPD70F3625(data flash) [DX3016]
uPD70F3625GK [DX3016]
uPD70F3625GK(data flash) [DX3016]
uPD70F3626 [DX3016]
uPD70F3626(data flash) [DX3016]
uPD70F3626GK [DX3016]
uPD70F3626GK(data flash) [DX3016]
uPD70F3627 [DX3043]
uPD70F3627(data flash) [DX3043]
uPD70F3627GK [DX3043]
uPD70F3627GK(data flash) [DX3043]
uPD70F3628 [DX3043]
uPD70F3628(data flash) [DX3043]
uPD70F3628GK [DX3043]
uPD70F3628GK(data flash) [DX3043]
uPD70F3629 [DX3043]
uPD70F3629(data flash) [DX3043]
uPD70F3629GK [DX3043]
uPD70F3629GK(data flash) [DX3043]
uPD70F3630 [DX3043]
uPD70F3630(data flash) [DX3043]
uPD70F3630GK [DX3043]
uPD70F3630GK(data flash) [DX3043]
uPD70F3631 [DX3051]
uPD70F3631(data flash) [DX3051]
uPD70F3631GK [DX3051]
uPD70F3631GK(data flash) [DX3051]
uPD70F3632 [DX3051]
uPD70F3632(data flash) [DX3051]
uPD70F3632GK [DX3051]
uPD70F3632GK(data flash) [DX3051]
uPD70F3633 [DX3051]
uPD70F3633(data flash) [DX3051]
uPD70F3633GK [DX3051]
uPD70F3633GK(data flash) [DX3051]
uPD70F3634 [DX3051]
uPD70F3634(data flash) [DX3051]
uPD70F3634GK [DX3051]
uPD70F3634GK(data flash) [DX3051]
uPD70F3635 [DX3051]
uPD70F3635(data flash) [DX3051]
uPD70F3635GK [DX3051]

uPD70F3635GK(data flash) [DX3051]
uPD70F3742GJA [DX3051]
uPD70F3743GJA [DX3051]
uPD70F3744GJA [DX3051]
uPD70F3745GJA [DX3051]
uPD70F3746GJA [DX3051]
uPD75P108BCW [DX0064]
uPD75P108BDW [DX0064]
uPD75P108BGF [DX3015]
uPD75P108CW [DX0064]
uPD75P108DW [DX0064]
uPD75P108GF [DX3015]
uPD75P116BCW [DX0064]
uPD75P116BDW [DX0064]
uPD75P116BGF [DX3015]
uPD75P116CW [DX0064]
uPD75P116DW [DX0064]
uPD75P116GF [DX3015]
uPD75P3018AGC [DX3018]
uPD75P3018AGK [DX3016]
uPD75P3018GC [DX3018]
uPD75P3018GK [DX3016]
uPD75P3036AGC [DX3018]
uPD75P3036AGK [DX3016]
uPD75P3036GC [DX3018]
uPD75P3036GK [DX3016]
UPD76F0168AGC [DX3014]
UPD76F0168GC [DX3014]
UPD76F9108AGC [DX3014]
UPD76F9108GC [DX3014]
uPD78F0034ACW [DX0064]
uPD78F0034AGB [DX3011]
uPD78F0034AGC [DX3013]
uPD78F0034AGK [DX3012]
uPD78F0034AYCW [DX0064]
uPD78F0034AYGB [DX3011]
uPD78F0034AYGC [DX3013]
uPD78F0034AYGK [DX3012]
uPD78F0034BCW [DX0064]
uPD78F0034BGB [DX3011]
uPD78F0034BGC [DX3013]
uPD78F0034BGK [DX3012]
uPD78F0034BYCW [DX0064]
uPD78F0034BYGB [DX3011]
uPD78F0034BYGC [DX3013]
uPD78F0034BYGK [DX3012]
uPD78F0034CW [DX0064]
uPD78F0034GB [DX3011]
uPD78F0034GC [DX3013]
uPD78F0034GK [DX3012]
uPD78F0400GA@LQFP48 [DX3047]
uPD78F0401GA@LQFP48 [DX3047]
uPD78F0402GA@LQFP48 [DX3047]
uPD78F0403GA@LQFP48 [DX3047]
uPD78F0404GA@LQFP48 [DX3047]
uPD78F0405GA@LQFP48 [DX3047]
uPD78F0410GA@LQFP48 [DX3047]
uPD78F0411GA@LQFP48 [DX3047]
uPD78F0412GA@LQFP48 [DX3047]
uPD78F0413GA@LQFP48 [DX3047]
uPD78F0414GA@LQFP48 [DX3047]
uPD78F0415GA@LQFP48 [DX3047]
uPD78F0500AAQS [DX1087]
uPD78F0500AAQSA [DX1087]
uPD78F0500AFC
uPD78F0500AMC [DX1087]
uPD78F0500AMCA [DX1087]
uPD78F0500AQS [DX1087]
uPD78F0500AQSA [DX1087]
uPD78F0500FC
uPD78F0500MC [DX1087]
uPD78F0500MCA [DX1087]
uPD78F0501AAQS [DX1087]
uPD78F0501AAQSA [DX1087]
uPD78F0501AFC
uPD78F0501AMC [DX1087]
uPD78F0501AMCA [DX1087]
uPD78F0501AQS [DX1087]
uPD78F0501AQSA [DX1087]
uPD78F0501FC
uPD78F0501MC [DX1087]
uPD78F0501MCA [DX1087]
uPD78F0502AAQS [DX1087]
uPD78F0502AAQSA [DX1087]
uPD78F0502AFC
uPD78F0502AMC [DX1087]
uPD78F0502AMCA [DX1087]
uPD78F0502AQS [DX1087]
uPD78F0502AQSA [DX1087]
uPD78F0502FC
uPD78F0502MC [DX1087]
uPD78F0502MCA [DX1087]
uPD78F0503AAQS [DX1087]
uPD78F0503AAQSA [DX1087]
uPD78F0503ADFC

uPD78F0503ADMC [DX1087]
uPD78F0503ADMCA [DX1087]
uPD78F0503AFC
uPD78F0503AMC [DX1087]
uPD78F0503AMCA [DX1087]
uPD78F0503AQS [DX1087]
uPD78F0503AQSA [DX1087]
uPD78F0503DFC
uPD78F0503DMC [DX1087]
uPD78F0503DMCA [DX1087]
uPD78F0503FC
uPD78F0503MC [DX1087]
uPD78F0503MCA [DX1087]
uPD78F0511AGA [DX3047]
uPD78F0511AGAA [DX3047]
uPD78F0511AGAA2 [DX3047]
uPD78F0511AGB [DX3005]
uPD78F0511AGBA [DX3005]
uPD78F0511AGBA2 [DX3005]
uPD78F0511AMC [DX1087]
uPD78F0511GA [DX3047]
uPD78F0511GAA [DX3047]
uPD78F0511GAA2 [DX3047]
uPD78F0511GB [DX3005]
uPD78F0511GBA [DX3005]
uPD78F0511GBA2 [DX3005]
uPD78F0511MC [DX1087]
uPD78F0512AGA [DX3047]
uPD78F0512AGAA [DX3047]
uPD78F0512AGAA2 [DX3047]
uPD78F0512AGB [DX3005]
uPD78F0512AGBA [DX3005]
uPD78F0512AGBA2 [DX3005]
uPD78F0512AMC [DX1087]
uPD78F0512GA [DX3047]
uPD78F0512GAA [DX3047]
uPD78F0512GAA2 [DX3047]
uPD78F0512GB [DX3005]
uPD78F0512GBA [DX3005]
uPD78F0512GBA2 [DX3005]
uPD78F0512MC [DX1087]
uPD78F0513ADGA [DX3047]
uPD78F0513ADGAA [DX3047]
uPD78F0513ADGAA2 [DX3047]
uPD78F0513ADGB [DX3005]
uPD78F0513ADGBA [DX3005]
uPD78F0513ADGBA2 [DX3005]
uPD78F0513ADMC [DX1087]
uPD78F0513AGA [DX3047]
uPD78F0513AGAA [DX3047]
uPD78F0513AGAA2 [DX3047]
uPD78F0513AGB [DX3005]
uPD78F0513AGBA [DX3005]
uPD78F0513AGBA2 [DX3005]
uPD78F0513AMC [DX1087]
uPD78F0513DGA [DX3047]
uPD78F0513DGAA [DX3047]
uPD78F0513DGAA2 [DX3047]
uPD78F0513DGB [DX3005]
uPD78F0513DGBA [DX3005]
uPD78F0513DGBA2 [DX3005]
uPD78F0513DMC [DX1087]
uPD78F0513GA [DX3047]
uPD78F0513GAA [DX3047]
uPD78F0513GAA2 [DX3047]
uPD78F0513GB [DX3005]
uPD78F0513GBA [DX3005]
uPD78F0513GBA2 [DX3005]
uPD78F0513MC [DX1087]
uPD78F0514AGA [DX3047]
uPD78F0514AGAA [DX3047]
uPD78F0514AGAA2 [DX3047]
uPD78F0514AGB [DX3005]
uPD78F0514AGBA [DX3005]
uPD78F0514AGBA2 [DX3005]
uPD78F0514AMC [DX1087]
uPD78F0514GA [DX3047]
uPD78F0514GAA [DX3047]
uPD78F0514GAA2 [DX3047]
uPD78F0514GB [DX3005]
uPD78F0514GBA [DX3005]
uPD78F0514GBA2 [DX3005]
uPD78F0514MC [DX1087]
uPD78F0515AGA [DX3047]
uPD78F0515AGAA [DX3047]
uPD78F0515AGAA2 [DX3047]
uPD78F0515AGB [DX3005]
uPD78F0515AGBA [DX3005]
uPD78F0515AGBA2 [DX3005]
uPD78F0515AMC [DX1087]
uPD78F0515GA [DX3047]
uPD78F0515GAA [DX3047]
uPD78F0515GAA2 [DX3047]
uPD78F0515GB [DX3005]
uPD78F0515GBA [DX3005]
uPD78F0515GBA2 [DX3005]

uPD78F0515MC [DX1087]
uPD78F0521AGB [DX3010]
uPD78F0521AGBA [DX3010]
uPD78F0521AGBA2 [DX3010]
uPD78F0521GB [DX3010]
uPD78F0521GBA [DX3010]
uPD78F0521GBA2 [DX3010]
uPD78F0522AGB [DX3010]
uPD78F0522AGBA [DX3010]
uPD78F0522AGBA2 [DX3010]
uPD78F0522GB [DX3010]
uPD78F0522GBA [DX3010]
uPD78F0522GBA2 [DX3010]
uPD78F0523ADGB [DX3010]
uPD78F0523ADGBA [DX3010]
uPD78F0523ADGBA2 [DX3010]
uPD78F0523AGB [DX3010]
uPD78F0523AGBA [DX3010]
uPD78F0523AGBA2 [DX3010]
uPD78F0523DGB [DX3010]
uPD78F0523DGBA [DX3010]
uPD78F0523DGBA2 [DX3010]
uPD78F0523GB [DX3010]
uPD78F0523GBA [DX3010]
uPD78F0523GBA2 [DX3010]
uPD78F0524AGB [DX3010]
uPD78F0524AGBA [DX3010]
uPD78F0524AGBA2 [DX3010]
uPD78F0524GB [DX3010]
uPD78F0524GBA [DX3010]
uPD78F0524GBA2 [DX3010]
uPD78F0525AGB [DX3010]
uPD78F0525AGBA [DX3010]
uPD78F0525AGBA2 [DX3010]
uPD78F0525GB [DX3010]
uPD78F0525GBA [DX3010]
uPD78F0525GBA2 [DX3010]
uPD78F0526AGB [DX3010]
uPD78F0526AGBA [DX3010]
uPD78F0526AGBA2 [DX3010]
uPD78F0526GB [DX3010]
uPD78F0526GBA [DX3010]
uPD78F0526GBA2 [DX3010]
uPD78F0527AGB [DX3010]
uPD78F0527AGBA [DX3010]
uPD78F0527AGBA2 [DX3010]
uPD78F0527GB [DX3010]
uPD78F0527GBA [DX3010]
uPD78F0527GBA2 [DX3010]
uPD78F0531AGB [DX3011]
uPD78F0531AGBA [DX3011]
uPD78F0531AGBA2 [DX3011]
uPD78F0531AGC [DX3013]
uPD78F0531AGCA [DX3013]
uPD78F0531AGCA2 [DX3013]
uPD78F0531AGK [DX3012]
uPD78F0531AGKA [DX3012]
uPD78F0531AGKA2 [DX3012]
uPD78F0531GA [DX3085]
uPD78F0531GB [DX3011]
uPD78F0531GBA [DX3011]
uPD78F0531GBA2 [DX3011]
uPD78F0531GC [DX3013]
uPD78F0531GCA [DX3013]
uPD78F0531GCA2 [DX3013]
uPD78F0531GK [DX3012]
uPD78F0531GKA [DX3012]
uPD78F0531GKA2 [DX3012]
uPD78F0532AGB [DX3011]
uPD78F0532AGBA [DX3011]
uPD78F0532AGBA2 [DX3011]
uPD78F0532AGC [DX3013]
uPD78F0532AGCA [DX3013]
uPD78F0532AGCA2 [DX3013]
uPD78F0532AGK [DX3012]
uPD78F0532AGKA [DX3012]
uPD78F0532AGKA2 [DX3012]
uPD78F0532GA [DX3085]
uPD78F0532GB [DX3011]
uPD78F0532GBA [DX3011]
uPD78F0532GBA2 [DX3011]
uPD78F0532GC [DX3013]
uPD78F0532GCA [DX3013]
uPD78F0532GCA2 [DX3013]
uPD78F0532GK [DX3012]
uPD78F0532GKA [DX3012]
uPD78F0532GKA2 [DX3012]
uPD78F0533ADGB [DX3011]
uPD78F0533ADGBA [DX3011]
uPD78F0533ADGBA2 [DX3011]
uPD78F0533ADGC [DX3013]
uPD78F0533ADGCA [DX3013]
uPD78F0533ADGCA2 [DX3013]
uPD78F0533ADGK [DX3012]
uPD78F0533ADGKA [DX3012]
uPD78F0533ADGKA2 [DX3012]

uPD78F0533AGB [DX3011]
uPD78F0533AGBA [DX3011]
uPD78F0533AGBA2 [DX3011]
uPD78F0533AGC [DX3013]
uPD78F0533AGCA [DX3013]
uPD78F0533AGCA2 [DX3013]
uPD78F0533AGK [DX3012]
uPD78F0533AGKA [DX3012]
uPD78F0533AGKA2 [DX3012]
uPD78F0533DGA [DX3085]
uPD78F0533DGB [DX3011]
uPD78F0533DGBA [DX3011]
uPD78F0533DGBA2 [DX3011]
uPD78F0533DGC [DX3013]
uPD78F0533DGCA [DX3013]
uPD78F0533DGCA2 [DX3013]
uPD78F0533DGK [DX3012]
uPD78F0533DGKA [DX3012]
uPD78F0533DGKA2 [DX3012]
uPD78F0533GA [DX3085]
uPD78F0533GB [DX3011]
uPD78F0533GBA [DX3011]
uPD78F0533GBA2 [DX3011]
uPD78F0533GC [DX3013]
uPD78F0533GCA [DX3013]
uPD78F0533GCA2 [DX3013]
uPD78F0533GK [DX3012]
uPD78F0533GKA [DX3012]
uPD78F0533GKA2 [DX3012]
uPD78F0534AGB [DX3011]
uPD78F0534AGBA [DX3011]
uPD78F0534AGBA2 [DX3011]
uPD78F0534AGC [DX3013]
uPD78F0534AGCA [DX3013]
uPD78F0534AGCA2 [DX3013]
uPD78F0534AGK [DX3012]
uPD78F0534AGKA [DX3012]
uPD78F0534AGKA2 [DX3012]
uPD78F0534GA [DX3085]
uPD78F0534GB [DX3011]
uPD78F0534GBA [DX3011]
uPD78F0534GBA2 [DX3011]
uPD78F0534GC [DX3013]
uPD78F0534GCA [DX3013]
uPD78F0534GCA2 [DX3013]
uPD78F0534GK [DX3012]
uPD78F0534GKA [DX3012]
uPD78F0534GKA2 [DX3012]
uPD78F0535AGB [DX3011]
uPD78F0535AGBA [DX3011]
uPD78F0535AGBA2 [DX3011]
uPD78F0535AGC [DX3013]
uPD78F0535AGCA [DX3013]
uPD78F0535AGCA2 [DX3013]
uPD78F0535AGK [DX3012]
uPD78F0535AGKA [DX3012]
uPD78F0535AGKA2 [DX3012]
uPD78F0535GA [DX3085]
uPD78F0535GB [DX3011]
uPD78F0535GBA [DX3011]
uPD78F0535GBA2 [DX3011]
uPD78F0535GC [DX3013]
uPD78F0535GCA [DX3013]
uPD78F0535GCA2 [DX3013]
uPD78F0535GK [DX3012]
uPD78F0535GKA [DX3012]
uPD78F0535GKA2 [DX3012]
uPD78F0536AGB [DX3011]
uPD78F0536AGBA [DX3011]
uPD78F0536AGBA2 [DX3011]
uPD78F0536AGC [DX3013]
uPD78F0536AGCA [DX3013]
uPD78F0536AGCA2 [DX3013]
uPD78F0536AGK [DX3012]
uPD78F0536AGKA [DX3012]
uPD78F0536AGKA2 [DX3012]
uPD78F0536GA [DX3085]
uPD78F0536GB [DX3011]
uPD78F0536GBA [DX3011]
uPD78F0536GBA2 [DX3011]
uPD78F0536GC [DX3013]
uPD78F0536GCA [DX3013]
uPD78F0536GCA2 [DX3013]
uPD78F0536GK [DX3012]
uPD78F0536GKA [DX3012]
uPD78F0536GKA2 [DX3012]
uPD78F0537ADGB [DX3011]
uPD78F0537ADGBA [DX3011]
uPD78F0537ADGBA2 [DX3011]
uPD78F0537ADGC [DX3013]
uPD78F0537ADGCA [DX3013]
uPD78F0537ADGCA2 [DX3013]
uPD78F0537ADGK [DX3012]
uPD78F0537ADGKA [DX3012]
uPD78F0537ADGKA2 [DX3012]
uPD78F0537AGB [DX3011]

uPD78F0537AGBA [DX3011]
uPD78F0537AGBA2 [DX3011]
uPD78F0537AGC [DX3013]
uPD78F0537AGCA [DX3013]
uPD78F0537AGCA2 [DX3013]
uPD78F0537AGK [DX3012]
uPD78F0537AGKA [DX3012]
uPD78F0537AGKA2 [DX3012]
uPD78F0537DGA [DX3085]
uPD78F0537DGB [DX3011]
uPD78F0537DGBA [DX3011]
uPD78F0537DGBA2 [DX3011]
uPD78F0537DGC [DX3013]
uPD78F0537DGCA [DX3013]
uPD78F0537DGCA2 [DX3013]
uPD78F0537DGK [DX3012]
uPD78F0537DGKA [DX3012]
uPD78F0537DGKA2 [DX3012]
uPD78F0537GA [DX3085]
uPD78F0537GB [DX3011]
uPD78F0537GBA [DX3011]
uPD78F0537GBA2 [DX3011]
uPD78F0537GC [DX3013]
uPD78F0537GCA [DX3013]
uPD78F0537GCA2 [DX3013]
uPD78F0537GK [DX3012]
uPD78F0537GKA [DX3012]
uPD78F0537GKA2 [DX3012]
uPD78F0544AGC [DX3017]
uPD78F0544AGCA [DX3017]
uPD78F0544AGCA2 [DX3017]
uPD78F0544AGK [DX3016]
uPD78F0544AGKA [DX3016]
uPD78F0544AGKA2 [DX3016]
uPD78F0544GC [DX3017]
uPD78F0544GCA [DX3017]
uPD78F0544GCA2 [DX3017]
uPD78F0544GK [DX3016]
uPD78F0544GKA [DX3016]
uPD78F0544GKA2 [DX3016]
uPD78F0545AGC [DX3017]
uPD78F0545AGCA [DX3017]
uPD78F0545AGCA2 [DX3017]
uPD78F0545AGK [DX3016]
uPD78F0545AGKA [DX3016]
uPD78F0545AGKA2 [DX3016]
uPD78F0545GC [DX3017]
uPD78F0545GCA [DX3017]
uPD78F0545GCA2 [DX3017]
uPD78F0545GK [DX3016]
uPD78F0545GKA [DX3016]
uPD78F0545GKA2 [DX3016]
uPD78F0546AGK [DX3016]
uPD78F0546AGKA [DX3016]
uPD78F0546AGKA2 [DX3016]
uPD78F0546GK [DX3016]
uPD78F0546GKA [DX3016]
uPD78F0546GKA2 [DX3016]
uPD78F0547ADGC [DX3017]
uPD78F0547ADGCA [DX3017]
uPD78F0547ADGCA2 [DX3017]
uPD78F0547ADGK [DX3016]
uPD78F0547ADGKA [DX3016]
uPD78F0547ADGKA2 [DX3016]
uPD78F0547AGC [DX3017]
uPD78F0547AGCA [DX3017]
uPD78F0547AGCA2 [DX3017]
uPD78F0547AGK [DX3016]
uPD78F0547AGKA [DX3016]
uPD78F0547AGKA2 [DX3016]
uPD78F0547DGC [DX3017]
uPD78F0547DGCA [DX3017]
uPD78F0547DGCA2 [DX3017]
uPD78F0547DGK [DX3016]
uPD78F0547DGKA [DX3016]
uPD78F0547DGKA2 [DX3016]
uPD78F0547GC [DX3017]
uPD78F0547GCA [DX3017]
uPD78F0547GCA2 [DX3017]
uPD78F0547GK [DX3016]
uPD78F0547GKA [DX3016]
uPD78F0547GKA2 [DX3016]
uPD78F0740MA [DX1016]
uPD78F0741MA [DX1016]
uPD78F0742MA [DX1016]
uPD78F0743MC [DX1027]
uPD78F0744MC [DX1027]
uPD78F0745MC [DX1027]
uPD78F0746MC [DX1027]
uPD78F0750MA [DX1016]
uPD78F0751MA [DX1016]
uPD78F0752MA [DX1016]
uPD78F0753MC [DX1027]
uPD78F0754MC [DX1027]
uPD78F0755MC [DX1027]
uPD78F0756MC [DX1027]

uPD78F0854MA [DX1001]
uPD78F0855MA [DX1001]
uPD78F0856MA [DX1001]
uPD78F0857MC [DX1027]
uPD78F0858MC [DX1027]
uPD78F0859MC [DX1027]
uPD78F0864MC [DX1027]
uPD78F0865MC [DX1027]
uPD78F0881AGBA [DX3002]
uPD78F0881AGBA2 [DX3002]
uPD78F0882AGBA [DX3002]
uPD78F0882AGBA2 [DX3002]
uPD78F0883AGBA [DX3002]
uPD78F0883AGBA2 [DX3002]
uPD78F0884AGAA [DX3007]
uPD78F0884AGAA2 [DX3007]
uPD78F0885AGAA [DX3007]
uPD78F0885AGAA2 [DX3007]
uPD78F0886AGAA [DX3007]
uPD78F0886AGAA2 [DX3007]
uPD78F0887AGBA [DX3011]
uPD78F0887AGBA2 [DX3011]
uPD78F0887AGKA [DX3012]
uPD78F0887AGKA2 [DX3012]
uPD78F0888AGBA [DX3011]
uPD78F0888AGBA2 [DX3011]
uPD78F0888AGKA [DX3012]
uPD78F0888AGKA2 [DX3012]
uPD78F0889AGBA [DX3011]
uPD78F0889AGBA2 [DX3011]
uPD78F0889AGKA [DX3012]
uPD78F0889AGKA2 [DX3012]
uPD78F0890AGBA [DX3011]
uPD78F0890AGBA2 [DX3011]
uPD78F0890AGKA [DX3012]
uPD78F0890AGKA2 [DX3012]
uPD78F0891AGCA [DX3016]
uPD78F0891AGCA2 [DX3016]
uPD78F0891AGKA [DX3018]
uPD78F0891AGKA2 [DX3018]
uPD78F0892AGCA [DX3016]
uPD78F0892AGCA2 [DX3016]
uPD78F0892AGKA [DX3018]
uPD78F0892AGKA2 [DX3018]
uPD78F0893AGCA [DX3016]
uPD78F0893AGCA2 [DX3016]
uPD78F0893AGKA [DX3018]
uPD78F0893AGKA2 [DX3018]
uPD78F0894AGAA [DX3007]
uPD78F0894AGAA2 [DX3007]
uPD78F0895AGAA [DX3007]
uPD78F0895AGAA2 [DX3007]
uPD78F1142AGA@TQFP64 [DX3064]
uPD78F1142AGB@LQFP64 [DX3011]
uPD78F1142AGK@LQFP64 [DX3012]
uPD78F1142GA@TQFP64 [DX3064]
uPD78F1142GB@LQFP64 [DX3011]
uPD78F1142GK@LQFP64 [DX3012]
uPD78F1143AGA@TQFP64 [DX3064]
uPD78F1143AGB [DX3011]
uPD78F1143AGK [DX3012]
uPD78F1143GA@TQFP64 [DX3064]
uPD78F1143GB@LQFP64 [DX3011]
uPD78F1143GK@LQFP64 [DX3012]
uPD78F1144AGA [DX3064]
uPD78F1144AGB [DX3011]
uPD78F1144AGK [DX3012]
uPD78F1144GA@TQFP64 [DX3064]
uPD78F1144GB@LQFP64 [DX3011]
uPD78F1144GK@LQFP64 [DX3012]
uPD78F1145AGA [DX3064]
uPD78F1145AGB [DX3011]
uPD78F1145AGK [DX3012]
uPD78F1145GA@TQFP64 [DX3064]
uPD78F1145GB@LQFP64 [DX3011]
uPD78F1145GK@LQFP64 [DX3012]
uPD78F1146AGA [DX3064]
uPD78F1146AGB [DX3011]
uPD78F1146AGK [DX3012]
uPD78F1146GA@TQFP64 [DX3064]
uPD78F1146GB@LQFP64 [DX3011]
uPD78F1146GK@LQFP64 [DX3012]
uPD78F1152AGC [DX3018]
uPD78F1152AGK [DX3016]
uPD78F1152GC@LQFP80 [DX3018]
uPD78F1152GK@LQFP80 [DX3016]
uPD78F1153AGC [DX3018]
uPD78F1153AGK [DX3016]
uPD78F1153GC@LQFP80 [DX3018]
uPD78F1153GK@LQFP80 [DX3016]
uPD78F1154AGC [DX3018]
uPD78F1154AGK [DX3016]
uPD78F1154GC@LQFP80 [DX3018]
uPD78F1154GK@LQFP80 [DX3016]
uPD78F1155AGC [DX3018]
uPD78F1155AGK [DX3016]

uPD78F1155GC@LQFP80 [DX3018]
uPD78F1155GK@LQFP80 [DX3016]
uPD78F1156AGC [DX3018]
uPD78F1156AGK [DX3016]
uPD78F1156GC@LQFP80 [DX3018]
uPD78F1156GK@LQFP80 [DX3016]
uPD78F1162@LQFP100 [DX3062]
uPD78F1162A [DX3062]
uPD78F1162AGC [DX3043]
uPD78F1162AGF [DX3062]
uPD78F1162GC@LQFP100 [DX3043]
uPD78F1162GF@LQFP100 [DX3062]
uPD78F1163@LQFP100 [DX3062]
uPD78F1163A [DX3062]
uPD78F1163AGC [DX3043]
uPD78F1163AGF [DX3062]
uPD78F1163GC@LQFP100 [DX3043]
uPD78F1163GF@LQFP100 [DX3062]
uPD78F1164@LQFP100 [DX3062]
uPD78F1164A [DX3062]
uPD78F1164AGC [DX3023]
uPD78F1164AGF [DX3062]
uPD78F1164GC@LQFP100 [DX3023]
uPD78F1164GF@LQFP100 [DX3062]
uPD78F1165@LQFP100 [DX3062]
uPD78F1165A [DX3062]
uPD78F1165AGC [DX3043]
uPD78F1165AGF [DX3062]
uPD78F1165GC@LQFP100 [DX3043]
uPD78F1165GF@LQFP100 [DX3062]
uPD78F1166@LQFP100 [DX3062]
uPD78F1166A [DX3062]
uPD78F1166AGC [DX3043]
uPD78F1166AGF [DX3062]
uPD78F1166GC@LQFP100 [DX3043]
uPD78F1166GF@LQFP100 [DX3062]
uPD78F1167@LQFP100 [DX3062]
uPD78F1167A [DX3062]
uPD78F1167AGC [DX3043]
uPD78F1167AGF [DX3062]
uPD78F1167GC@LQFP100 [DX3043]
uPD78F1167GF@LQFP100 [DX3062]
uPD78F1168@LQFP100 [DX3062]
uPD78F1168A [DX3062]
uPD78F1168AGC [DX3043]
uPD78F1168AGF [DX3062]
uPD78F1168GC@LQFP100 [DX3043]
uPD78F1168GF@LQFP100 [DX3062]
uPD78F1804AK8 [DX4015]
uPD78F1804AK8A [DX4015]
uPD78F1804AK8A2 [DX4015]
uPD78F1804AMC [DX1027]
uPD78F1804AMCA [DX1027]
uPD78F1804AMCA2 [DX1027]
uPD78F1804K8 [DX4015]
uPD78F1804K8A [DX4015]
uPD78F1804K8A2 [DX4015]
uPD78F1804MC [DX1027]
uPD78F1804MCA [DX1027]
uPD78F1804MCA2 [DX1027]
uPD78F1805AK8 [DX4015]
uPD78F1805AK8A [DX4015]
uPD78F1805AK8A2 [DX4015]
uPD78F1805AMC [DX1027]
uPD78F1805AMCA [DX1027]
uPD78F1805AMCA2 [DX1027]
uPD78F1805K8 [DX4015]
uPD78F1805K8A [DX4015]
uPD78F1805K8A2 [DX4015]
uPD78F1805MC [DX1027]
uPD78F1805MCA [DX1027]
uPD78F1805MCA2 [DX1027]
uPD78F1806AK8 [DX4015]
uPD78F1806AK8A [DX4015]
uPD78F1806AK8A2 [DX4015]
uPD78F1806AMC [DX1027]
uPD78F1806AMCA [DX1027]
uPD78F1806AMCA2 [DX1027]
uPD78F1806K8 [DX4015]
uPD78F1806K8A [DX4015]
uPD78F1806K8A2 [DX4015]
uPD78F1806MC [DX1027]
uPD78F1806MCA [DX1027]
uPD78F1806MCA2 [DX1027]
uPD78F1807AK8 [DX4015]
uPD78F1807AK8A [DX4015]
uPD78F1807AK8A2 [DX4015]
uPD78F1807AMC [DX1027]
uPD78F1807AMCA [DX1027]
uPD78F1807AMCA2 [DX1027]
uPD78F1807K8 [DX4015]
uPD78F1807K8A [DX4015]
uPD78F1807K8A2 [DX4015]
uPD78F1807MC [DX1027]
uPD78F1807MCA [DX1027]
uPD78F1807MCA2 [DX1027]

uPD78F1808AK8 [DX4017]
uPD78F1808AK8A [DX4017]
uPD78F1808AK8A2 [DX4017]
uPD78F1808K8 [DX4017]
uPD78F1808K8A [DX4017]
uPD78F1808K8A2 [DX4017]
uPD78F1809AK8 [DX4017]
uPD78F1809AK8A [DX4017]
uPD78F1809AK8A2 [DX4017]
uPD78F1809K8 [DX4017]
uPD78F1809K8A [DX4017]
uPD78F1809K8A2 [DX4017]
uPD78F1810AK8 [DX4017]
uPD78F1810AK8A [DX4017]
uPD78F1810AK8A2 [DX4017]
uPD78F1810K8 [DX4017]
uPD78F1810K8A [DX4017]
uPD78F1810K8A2 [DX4017]
uPD78F1811AK8 [DX4017]
uPD78F1811AK8A [DX4017]
uPD78F1811AK8A2 [DX4017]
uPD78F1811K8 [DX4017]
uPD78F1811K8A [DX4017]
uPD78F1811K8A2 [DX4017]
uPD78F1812AGA [DX3007]
uPD78F1812AGAA [DX3007]
uPD78F1812AGAA2 [DX3007]
uPD78F1812AK8 [DX3007]
uPD78F1812AK8A [DX3007]
uPD78F1812AK8A2 [DX3007]
uPD78F1812GA [DX3007]
uPD78F1812GAA [DX3007]
uPD78F1812GAA2 [DX3007]
uPD78F1812K8 [DX3007]
uPD78F1812K8A [DX3007]
uPD78F1812K8A2 [DX3007]
uPD78F1813AGA [DX3007]
uPD78F1813AGAA [DX3007]
uPD78F1813AGAA2 [DX3007]
uPD78F1813AK8 [DX3007]
uPD78F1813AK8A [DX3007]
uPD78F1813AK8A2 [DX3007]
uPD78F1813GA [DX3007]
uPD78F1813GAA [DX3007]
uPD78F1813GAA2 [DX3007]
uPD78F1813K8 [DX3007]
uPD78F1813K8A [DX3007]
uPD78F1813K8A2 [DX3007]
uPD78F1814AGA [DX3007]
uPD78F1814AGAA [DX3007]
uPD78F1814AGAA2 [DX3007]
uPD78F1814AK8 [DX3007]
uPD78F1814AK8A [DX3007]
uPD78F1814AK8A2 [DX3007]
uPD78F1814GA [DX3007]
uPD78F1814GAA [DX3007]
uPD78F1814GAA2 [DX3007]
uPD78F1814K8 [DX3007]
uPD78F1814K8A [DX3007]
uPD78F1814K8A2 [DX3007]
uPD78F1815AGA [DX3007]
uPD78F1815AGAA [DX3007]
uPD78F1815AGAA2 [DX3007]
uPD78F1815AK8 [DX3007]
uPD78F1815AK8A [DX3007]
uPD78F1815AK8A2 [DX3007]
uPD78F1815GA [DX3007]
uPD78F1815GAA [DX3007]
uPD78F1815GAA2 [DX3007]
uPD78F1815K8 [DX3007]
uPD78F1815K8A [DX3007]
uPD78F1815K8A2 [DX3007]
uPD78F1816AGA [DX3007]
uPD78F1816AGAA [DX3007]
uPD78F1816AGAA2 [DX3007]
uPD78F1816AK8 [DX3007]
uPD78F1816AK8A [DX3007]
uPD78F1816AK8A2 [DX3007]
uPD78F1816GA [DX3007]
uPD78F1816GAA [DX3007]
uPD78F1816GAA2 [DX3007]
uPD78F1816K8 [DX3007]
uPD78F1816K8A [DX3007]
uPD78F1816K8A2 [DX3007]
uPD78F1817AGA [DX3007]
uPD78F1817AGAA [DX3007]
uPD78F1817AGAA2 [DX3007]
uPD78F1817AK8 [DX3007]
uPD78F1817AK8A [DX3007]
uPD78F1817AK8A2 [DX3007]
uPD78F1817GA [DX3007]
uPD78F1817GAA [DX3007]
uPD78F1817GAA2 [DX3007]
uPD78F1817K8 [DX3007]
uPD78F1817K8A [DX3007]
uPD78F1817K8A2 [DX3007]

uPD78F1818AGB [DX3011]
uPD78F1818AGBA [DX3011]
uPD78F1818AGBA2 [DX3011]
uPD78F1818GB [DX3011]
uPD78F1818GBA [DX3011]
uPD78F1818GBA2 [DX3011]
uPD78F1819AGB [DX3011]
uPD78F1819AGBA [DX3011]
uPD78F1819AGBA2 [DX3011]
uPD78F1819GB [DX3011]
uPD78F1819GBA [DX3011]
uPD78F1819GBA2 [DX3011]
uPD78F1820AGB [DX3011]
uPD78F1820AGBA [DX3011]
uPD78F1820AGBA2 [DX3011]
uPD78F1820GB [DX3011]
uPD78F1820GBA [DX3011]
uPD78F1820GBA2 [DX3011]
uPD78F1821AGB [DX3011]
uPD78F1821AGBA [DX3011]
uPD78F1821AGBA2 [DX3011]
uPD78F1821GB [DX3011]
uPD78F1821GBA [DX3011]
uPD78F1821GBA2 [DX3011]
uPD78F1822AGB [DX3011]
uPD78F1822AGBA [DX3011]
uPD78F1822AGBA2 [DX3011]
uPD78F1822GB [DX3011]
uPD78F1822GBA [DX3011]
uPD78F1822GBA2 [DX3011]
uPD78F1823AGK [DX3016]
uPD78F1823AGKA [DX3016]
uPD78F1823AGKA2 [DX3016]
uPD78F1823GK [DX3016]
uPD78F1823GKA [DX3016]
uPD78F1823GKA2 [DX3016]
uPD78F1824AGK [DX3016]
uPD78F1824AGKA [DX3016]
uPD78F1824AGKA2 [DX3016]
uPD78F1824GK [DX3016]
uPD78F1824GKA [DX3016]
uPD78F1824GKA2 [DX3016]
uPD78F1825AGK [DX3016]
uPD78F1825AGKA [DX3016]
uPD78F1825AGKA2 [DX3016]
uPD78F1825GK [DX3016]
uPD78F1825GKA [DX3016]
uPD78F1825GKA2 [DX3016]
uPD78F1826AGA [DX3007]
uPD78F1826AGAA [DX3007]
uPD78F1826AGAA2 [DX3007]
uPD78F1826AK8 [DX3007]
uPD78F1826AK8A [DX3007]
uPD78F1826AK8A2 [DX3007]
uPD78F1826GA [DX3007]
uPD78F1826GAA [DX3007]
uPD78F1826GAA2 [DX3007]
uPD78F1826K8 [DX3007]
uPD78F1826K8A [DX3007]
uPD78F1826K8A2 [DX3007]
uPD78F1827AGA [DX3007]
uPD78F1827AGAA [DX3007]
uPD78F1827AGAA2 [DX3007]
uPD78F1827AK8 [DX3007]
uPD78F1827AK8A [DX3007]
uPD78F1827AK8A2 [DX3007]
uPD78F1827GA [DX3007]
uPD78F1827GAA [DX3007]
uPD78F1827GAA2 [DX3007]
uPD78F1827K8 [DX3007]
uPD78F1827K8A [DX3007]
uPD78F1827K8A2 [DX3007]
uPD78F1828AGA [DX3007]
uPD78F1828AGAA [DX3007]
uPD78F1828AGAA2 [DX3007]
uPD78F1828AK8 [DX3007]
uPD78F1828AK8A [DX3007]
uPD78F1828AK8A2 [DX3007]
uPD78F1828GA [DX3007]
uPD78F1828GAA [DX3007]
uPD78F1828GAA2 [DX3007]
uPD78F1828K8 [DX3007]
uPD78F1828K8A [DX3007]
uPD78F1828K8A2 [DX3007]
uPD78F1829AGA [DX3007]
uPD78F1829AGAA [DX3007]
uPD78F1829AGAA2 [DX3007]
uPD78F1829AK8 [DX3007]
uPD78F1829AK8A [DX3007]
uPD78F1829AK8A2 [DX3007]
uPD78F1829GA [DX3007]
uPD78F1829GAA [DX3007]
uPD78F1829GAA2 [DX3007]
uPD78F1829K8 [DX3007]
uPD78F1829K8A [DX3007]
uPD78F1829K8A2 [DX3007]

uPD78F1830AGA [DX3007]
uPD78F1830AGAA [DX3007]
uPD78F1830AGAA2 [DX3007]
uPD78F1830AK8 [DX3007]
uPD78F1830AK8A [DX3007]
uPD78F1830AK8A2 [DX3007]
uPD78F1830GA [DX3007]
uPD78F1830GAA [DX3007]
uPD78F1830GAA2 [DX3007]
uPD78F1830K8 [DX3007]
uPD78F1830K8A [DX3007]
uPD78F1830K8A2 [DX3007]
uPD78F1831AGB [DX3011]
uPD78F1831AGBA [DX3011]
uPD78F1831AGBA2 [DX3011]
uPD78F1831GB [DX3011]
uPD78F1831GBA [DX3011]
uPD78F1831GBA2 [DX3011]
uPD78F1832AGB [DX3011]
uPD78F1832AGBA [DX3011]
uPD78F1832AGBA2 [DX3011]
uPD78F1832GB [DX3011]
uPD78F1832GBA [DX3011]
uPD78F1832GBA2 [DX3011]
uPD78F1833AGB [DX3011]
uPD78F1833AGBA [DX3011]
uPD78F1833AGBA2 [DX3011]
uPD78F1833GB [DX3011]
uPD78F1833GBA [DX3011]
uPD78F1833GBA2 [DX3011]
uPD78F1834AGB [DX3011]
uPD78F1834AGBA [DX3011]
uPD78F1834AGBA2 [DX3011]
uPD78F1834GB [DX3011]
uPD78F1834GBA [DX3011]
uPD78F1834GBA2 [DX3011]
uPD78F1835AGB [DX3011]
uPD78F1835AGBA [DX3011]
uPD78F1835AGBA2 [DX3011]
uPD78F1835GB [DX3011]
uPD78F1835GBA [DX3011]
uPD78F1835GBA2 [DX3011]
uPD78F1836AGK [DX3016]
uPD78F1836AGKA [DX3016]
uPD78F1836AGKA2 [DX3016]
uPD78F1836GK [DX3016]
uPD78F1836GKA [DX3016]
uPD78F1836GKA2 [DX3016]
uPD78F1837AGK [DX3016]
uPD78F1837AGKA [DX3016]
uPD78F1837AGKA2 [DX3016]
uPD78F1837GK [DX3016]
uPD78F1837GKA [DX3016]
uPD78F1837GKA2 [DX3016]
uPD78F1838AGK [DX3016]
uPD78F1838AGKA [DX3016]
uPD78F1838AGKA2 [DX3016]
uPD78F1838GK [DX3016]
uPD78F1838GKA [DX3016]
uPD78F1838GKA2 [DX3016]
uPD78F1839AGK [DX3016]
uPD78F1839AGKA [DX3016]
uPD78F1839AGKA2 [DX3016]
uPD78F1839GK [DX3016]
uPD78F1839GKA [DX3016]
uPD78F1839GKA2 [DX3016]
uPD78F1840AGK [DX3021]
uPD78F1840AGKA [DX3021]
uPD78F1840AGKA2 [DX3021]
uPD78F1840GK [DX3021]
uPD78F1840GKA [DX3021]
uPD78F1840GKA2 [DX3021]
uPD78F1841AGK [DX3021]
uPD78F1841AGKA [DX3021]
uPD78F1841AGKA2 [DX3021]
uPD78F1841GK [DX3021]
uPD78F1841GKA [DX3021]
uPD78F1841GKA2 [DX3021]
uPD78F1842AGK [DX3021]
uPD78F1842AGKA [DX3021]
uPD78F1842AGKA2 [DX3021]
uPD78F1842GK [DX3021]
uPD78F1842GKA [DX3021]
uPD78F1842GKA2 [DX3021]
uPD78F1843AGK [DX3021]
uPD78F1843AGKA [DX3021]
uPD78F1843AGKA2 [DX3021]
uPD78F1843GK [DX3021]
uPD78F1843GKA [DX3021]
uPD78F1843GKA2 [DX3021]
uPD78F1844AGK [DX3021]
uPD78F1844AGKA [DX3021]
uPD78F1844AGKA2 [DX3021]
uPD78F1844GK [DX3021]
uPD78F1844GKA [DX3021]
uPD78F1844GKA2 [DX3021]

uPD78F1845AGK [DX3021]
uPD78F1845AGKA [DX3021]
uPD78F1845AGKA2 [DX3021]
uPD78F1845GK [DX3021]
uPD78F1845GKA [DX3021]
uPD78F1845GKA2 [DX3021]
uPD78F9025@SDIP42 [DX0042]
uPD78F9025@TQFP44 [DX3002]
uPD78F9025A@SDIP42 [DX0042]
uPD78F9025A@TQFP44 [DX3002]
uPD78F9025B@SDIP42 [DX0042]
uPD78F9025B@TQFP44 [DX3002]
uPD78F9026@SDIP42 [DX0042]
uPD78F9026@TQFP44 [DX3002]
uPD78F9026A@SDIP42 [DX0042]
uPD78F9026A@TQFP44 [DX3002]
uPD78F9026B@SDIP42 [DX0042]
uPD78F9026B@TQFP44 [DX3002]
uPD78F9045@SDIP42 [DX0042]
uPD78F9045@TQFP44 [DX3002]
uPD78F9045A@SDIP42 [DX0042]
uPD78F9045A@TQFP44 [DX3002]
uPD78F9045B@SDIP42 [DX0042]
uPD78F9045B@TQFP44 [DX3002]
uPD78F9046@SDIP42 [DX0042]
uPD78F9046@TQFP44 [DX3002]
uPD78F9046A@SDIP42 [DX0042]
uPD78F9046A@TQFP44 [DX3002]
uPD78F9046B@SDIP42 [DX0042]
uPD78F9046B@TQFP44 [DX3002]
uPD78F9177@LQFP44 [DX3005]
uPD78F9177@QFP48 [DX3007]
uPD78F9177@SDIP42 [DX0042]
uPD78F9177A@LQFP44 [DX3005]
uPD78F9177A@QFP48 [DX3007]
uPD78F9177A@SDIP42 [DX0042]
uPD78F9177AY@LQFP44 [DX3005]
uPD78F9177AY@QFP48 [DX3007]
uPD78F9177AY@SDIP42 [DX0042]
uPD78F9177C@LQFP44 [DX3005]
uPD78F9177C@QFP48 [DX3007]
uPD78F9177C@SDIP42 [DX0042]
uPD78F9177Y@LQFP44 [DX3005]
uPD78F9177Y@QFP48 [DX3007]
uPD78F9177Y@SDIP42 [DX0042]
uPD78F9328GB [DX3010]
uPD78P214CW [DX0064]
uPD78P214L [DX2168]
uPD78P218CW [DX0064]
uPD78P218L [DX2168]
uPD78P368AGF [DX3019]
uPD79F7020GB [DX3010]
UPD79F7023MC [DX1074]
UPD79F7024MC [DX1074]
UPD79F7025@QFP32 [DX3001]
UPD79F7026@QFP32 [DX3001]
uPD79F8525AGB [DX3010]
uPD79F8525AGBA [DX3010]
uPD79F8525AGBA2 [DX3010]
uPD79F8525GB [DX3010]
uPD79F8525GBA [DX3010]
uPD79F8525GBA2 [DX3010]

RICHTEK

E(E)PROM/FRAM/NVRAM

RT6729@QFN28 [DX4036]

MICROCONTROLLER

CM601@QFN24 [DX4012]
CM602@QFN28 [DX4013]
RT4527@QFN20 [DX4094]
RT4527@QFN20(left down) [DX4094]
RT6505@QFN28 [DX4036]
RT6505@QFN28(left down) [DX4036]
RT6547 [DX0001]
RT6716@WLCSP48 [DX5238]
RT6735@WQFN40 [DX4095]
RT6914@QFN40 [DX4017]
RT6914@QFN40(left down) [DX4017]

RICOH

E(E)PROM/FRAM/NVRAM

RD27C256 [DX0001]
RD27C32 [DX0001]
RD27C64 [DX0001]

ROCKWELL

E(E)PROM/FRAM/NVRAM

R2764 [DX0001]
R2764C [DX0001]
R2764P [DX0001]
R27C64 [DX0001]
R2816 [DX0001]
R5213 [DX0001]
R52B13 [DX0001]
R52B33 [DX0001]

ROHM

E(E)PROM/FRAM/NVRAM

BH9020 [DX1045]
BR24A01A(F) [DX1079]
BR24A01A(FJ) [DX1079]
BR24A02(F) [DX1079]
BR24A02(FJ) [DX1079]
BR24A04(F) [DX1079]
BR24A04(FJ) [DX1079]
BR24A08(F) [DX1079]
BR24A08(FJ) [DX1079]
BR24A16(F) [DX1079]
BR24A16(FJ) [DX1079]
BR24A32(F) [DX1079]
BR24A32(FJ) [DX1079]
BR24A64(F) [DX1079]
BR24A64(FJ) [DX1079]
BR24C01@SOP8 [DX1079]
BR24C01@TSSOP8 [DX1059]
BR24C01@TSSOP8(3*3mm) [DX1015]
BR24C01A [DX0001]
BR24C01A(F) [DX1079]
BR24C01A(FJ) [DX1079]
BR24C01A(FV) [DX1059]
BR24C02 [DX0001]
BR24C02(F) [DX1079]
BR24C02(FJ) [DX1079]
BR24C02(FV) [DX1059]
BR24C02@SOP8 [DX1079]
BR24C02@TSSOP8 [DX1059]
BR24C02@TSSOP8(3*3mm) [DX1015]
BR24C04 [DX0001]
BR24C04(F) [DX1079]
BR24C04(FJ) [DX1079]
BR24C04(FV) [DX1059]
BR24C04@SOP8 [DX1079]
BR24C04@TSSOP8 [DX1059]
BR24C04@TSSOP8(3*3mm) [DX1015]
BR24C08 [DX0001]
BR24C08(F) [DX1079]
BR24C08(FJ) [DX1079]
BR24C08(FV) [DX1059]
BR24C08@SOP8 [DX1079]
BR24C08@TSSOP8 [DX1059]
BR24C08@TSSOP8(3*3mm) [DX1015]
BR24C16 [DX0001]
BR24C16(F) [DX1079]
BR24C16(FJ) [DX1079]
BR24C16(FV) [DX1059]
BR24C21 [DX0001]

BR24C21(F) [DX1079]
BR24C21(FJ) [DX1079]
BR24C21(FV) [DX1059]
BR24C32 [DX0001]
BR24C32(F) [DX1079]
BR24C64 [DX0001]
BR24C64(F) [DX1079]
BR24E16 [DX0001]
BR24E16(F) [DX1079]
BR24E16(FJ) [DX1079]
BR24E16(FV) [DX1059]
BR24G01 [DX0001]
BR24G01(F) [DX1079]
BR24G01(FJ) [DX1079]
BR24G01(FV) [DX1059]
BR24G02 [DX0001]
BR24G02(F) [DX1079]
BR24G02(FJ) [DX1079]
BR24G02(FV) [DX1059]
BR24G04 [DX0001]
BR24G04(F) [DX1079]
BR24G04(FJ) [DX1079]
BR24G04(FV) [DX1059]
BR24G08(F) [DX1079]
BR24G08(FJ) [DX1079]
BR24G08(FV) [DX1059]
BR24G08(FVJ) [DX1059]
BR24G08(FVM) [DX1015]
BR24G08(FVT) [DX1059]
BR24G128 [DX0001]
BR24G128(F) [DX1079]
BR24G128(FJ) [DX1079]
BR24G128(FV) [DX1059]
BR24G128(FVT) [DX1059]
BR24G16 [DX0001]
BR24G16(F) [DX1079]
BR24G16(FJ) [DX1079]
BR24G16(FV) [DX1059]
BR24G16(FVM) [DX1015]
BR24G256 [DX0001]
BR24G256(F) [DX1079]
BR24G256(FJ) [DX1079]
BR24G256(FV) [DX1059]
BR24G256(FVT) [DX1059]
BR24G32 [DX0001]
BR24G32(F) [DX1079]
BR24G32(FJ) [DX1079]
BR24G32(FV) [DX1059]
BR24G32(FVT) [DX1059]
BR24G512 [DX0001]
BR24G512F [DX1048]
BR24G512FJ [DX1079]
BR24G512FV [DX1059]
BR24G512FVT [DX1059]
BR24G64 [DX0001]
BR24G64(F) [DX1079]
BR24G64(FJ) [DX1079]
BR24G64(FV) [DX1059]
BR24G64(FVT) [DX1059]
BR24L01A [DX0001]
BR24L01A(F) [DX1079]
BR24L01A(FJ) [DX1079]
BR24L01A(FV) [DX1059]
BR24L01A(FVM) [DX1015]
BR24L01A@VSON8 [DX4047]
BR24L02 [DX0001]
BR24L02(F) [DX1079]
BR24L02(FJ) [DX1079]
BR24L02(FV) [DX1059]
BR24L02(FVM) [DX1015]
BR24L02@VSON8 [DX4047]
BR24L04 [DX0001]
BR24L04(F) [DX1079]
BR24L04(FJ) [DX1079]
BR24L04(FV) [DX1059]
BR24L04(FVM) [DX1015]
BR24L04@VSON8 [DX4047]
BR24L08 [DX0001]
BR24L08(F) [DX1079]
BR24L08(FJ) [DX1079]
BR24L08(FV) [DX1059]
BR24L08(FVM) [DX1015]
BR24L08@VSON8 [DX4047]
BR24L16 [DX0001]
BR24L16(F) [DX1079]
BR24L16(FJ) [DX1079]
BR24L16(FV) [DX1059]
BR24L16(FVM) [DX1015]
BR24L32 [DX0001]
BR24L32(F) [DX1079]
BR24L32(FJ) [DX1079]
BR24L32(FV) [DX1059]
BR24L64 [DX0001]
BR24L64(F) [DX1079]
BR24L64(FJ) [DX1079]
BR24L64(FV) [DX1059]

BR24S08(F) [DX1079]
BR24S08(FJ) [DX1079]
BR24S08(FV) [DX1059]
BR24S08(FVJ) [DX1059]
BR24S08(FVM) [DX1015]
BR24S08(FVT) [DX1059]
BR24S128 [DX0001]
BR24S128(F) [DX1079]
BR24S128(FJ) [DX1079]
BR24S128(FV) [DX1059]
BR24S16 [DX0001]
BR24S16(F) [DX1079]
BR24S16(FJ) [DX1079]
BR24S16(FV) [DX1059]
BR24S16(FVM) [DX1015]
BR24S256 [DX0001]
BR24S256(F) [DX1079]
BR24S256(FJ) [DX1079]
BR24S256(FV) [DX1059]
BR24S32 [DX0001]
BR24S32(F) [DX1079]
BR24S32(FJ) [DX1079]
BR24S32(FV) [DX1059]
BR24S64 [DX0001]
BR24S64(F) [DX1079]
BR24S64(FJ) [DX1079]
BR24S64(FV) [DX1059]
BR24T01 [DX0001]
BR24T01(F) [DX1079]
BR24T01(FJ) [DX1079]
BR24T01(FV) [DX1059]
BR24T02 [DX0001]
BR24T02(F) [DX1079]
BR24T02(FJ) [DX1079]
BR24T02(FV) [DX1059]
BR24T02@VSON8 [DX4047]
BR24T04 [DX0001]
BR24T04(F) [DX1079]
BR24T04(FJ) [DX1079]
BR24T04(FV) [DX1059]
BR24T08(F) [DX1079]
BR24T08(FJ) [DX1079]
BR24T08(FV) [DX1059]
BR24T08(FVJ) [DX1059]
BR24T08(FVM) [DX1015]
BR24T08(FVT) [DX1059]
BR24T128 [DX0001]
BR24T128(F) [DX1079]
BR24T128(FJ) [DX1079]
BR24T128(FV) [DX1059]
BR24T128(FVT) [DX1059]
BR24T16 [DX0001]
BR24T16(F) [DX1079]
BR24T16(FJ) [DX1045]
BR24T16(FV) [DX1059]
BR24T16(FVM) [DX1015]
BR24T16@VSON8 [DX4047]
BR24T1M [DX0001]
BR24T1MF [DX1044]
BR24T256 [DX0001]
BR24T256(F) [DX1079]
BR24T256(FJ) [DX1079]
BR24T256(FV) [DX1059]
BR24T256(FVT) [DX1059]
BR24T32 [DX0001]
BR24T32(F) [DX1079]
BR24T32(FJ) [DX1079]
BR24T32(FV) [DX1059]
BR24T32(FVT) [DX1059]
BR24T32@VSON8 [DX4047]
BR24T512 [DX0001]
BR24T512(F) [DX1048]
BR24T512(FJ) [DX1079]
BR24T512(FV) [DX1059]
BR24T512(FVT) [DX1059]
BR24T64 [DX0001]
BR24T64(F) [DX1079]
BR24T64(FJ) [DX1079]
BR24T64(FV) [DX1059]
BR24T64(FVT) [DX1059]
BR25010@SOIC8 [DX1045]
BR25010@TSSOP8 [DX1059]
BR25020@SOIC8 [DX1045]
BR25020@TSSOP8 [DX1059]
BR25040@SOIC8 [DX1045]
BR25040@TSSOP8 [DX1059]
BR25080@SOIC8 [DX1045]
BR25080@TSSOP8 [DX1059]
BR25160@SOIC8 [DX1045]
BR25160@TSSOP8 [DX1059]
BR25320@SOIC8 [DX1045]
BR25G1MF [DX1045]
BR25G1MFJ [DX1045]
BR25H010(F) [DX1045]
BR25H010(FJ) [DX1045]
BR25H020(F) [DX1045]

BR25H020(FJ) [DX1045]
BR25H040(FJ) [DX1045]
BR25H080(FJ) [DX1045]
BR25H160(F) [DX1045]
BR25H160(FVT) [DX1059]
BR25H320(FJ) [DX1045]
BR25L010 [DX0001]
BR25L010(FJ) [DX1045]
BR25L010(FVM) [DX1015]
BR25L020(F) [DX1045]
BR25L020(FV) [DX1059]
BR25L040 [DX0001]
BR25L040(FJ) [DX1045]
BR25L040(FVM) [DX1015]
BR25L080(F) [DX1045]
BR25L080(FV) [DX1059]
BR25L160(F) [DX1045]
BR25L160(FV) [DX1059]
BR25L320(F) [DX1045]
BR25L320(FV) [DX1059]
BR25L640(F) [DX1045]
BR25L640(FV) [DX1059]
BR25S128FJ [DX1045]
BR25S128FVT [DX1059]
BR25S256FJ [DX1045]
BR25S320FJ [DX1045]
BR25S320FVJ [DX1015]
BR25S320FVT [DX1059]
BR25S640F [DX1079]
BR25S640FV [DX1059]
BR25S640FVM [DX1015]
BR34C02A [DX1059]
BR34L02(F) [DX1045]
BR34L02(FV) [DX1059]
BR35H010F [DX1079]
BR35H020F [DX1079]
BR35H040F [DX1079]
BR35H080F [DX1079]
BR35H080FVT [DX1059]
BR35H128FJ [DX1045]
BR35H160FJ [DX1045]
BR35H160FVT [DX1059]
BR35H320FJ [DX1045]
BR35H320FVT [DX1059]
BR35H640FJ [DX1045]
BR9010 [DX0001]
BR9010(FV) [DX1059]
BR9010(RFVM) [DX1015]
BR25H040(F) [DX1045]
BR25H080(F) [DX1045]
BR25H080(FVT) [DX1059]
BR25H160(FJ) [DX1045]
BR25H320(F) [DX1045]
BR25H320(FVT) [DX1059]
BR25L010(F) [DX1045]
BR25L010(FV) [DX1059]
BR25L020 [DX0001]
BR25L020(FJ) [DX1045]
BR25L020(FVM) [DX1015]
BR25L040(F) [DX1045]
BR25L040(FV) [DX1059]
BR25L080 [DX0001]
BR25L080(FJ) [DX1045]
BR25L160 [DX0001]
BR25L160(FJ) [DX1045]
BR25L320 [DX0001]
BR25L320(FJ) [DX1045]
BR25L640 [DX0001]
BR25L640(FJ) [DX1045]
BR25S128F [DX1079]
BR25S128FV [DX1059]
BR25S256F [DX1079]
BR25S320F [DX1079]
BR25S320FV [DX1059]
BR25S320FVM [DX1015]
BR25S320NUX [DX4002]
BR25S640FJ [DX1045]
BR25S640FVJ [DX1015]
BR25S640FVT [DX1059]
BR34L02 [DX0001]
BR34L02(FJ) [DX1045]
BR34L02(FVM) [DX1015]
BR35H010FJ [DX1045]
BR35H020FJ [DX1045]
BR35H040FJ [DX1045]
BR35H080FJ [DX1045]
BR35H128F [DX1079]
BR35H160F [DX1079]
BR35H160FVM [DX1015]
BR35H320F [DX1079]
BR35H320FVM [DX1015]
BR35H640F [DX1079]
BR35H640FVT [DX1059]
BR9010(F) [DX1045]
BR9010(RFV) [DX1059]
BR9016 [DX0001]

BR9016(F) [DX1045]
BR9016A(F) [DX1045]
BR9016A(RFVM) [DX1015]
BR9020(F) [DX1045]
BR9020(RFV) [DX1059]
BR9040 [DX0001]
BR9040(FV) [DX1059]
BR9040(RFVM) [DX1015]
BR9080(F) [DX1045]
BR9080A [DX0001]
BR9080A(FV) [DX1059]
BR9080A(RFVM) [DX1015]
BR93A46(FJ) [DX1045]
BR93A46(RFJ) [DX1045]
BR93A56(FJ) [DX1045]
BR93A56(RFJ) [DX1045]
BR93A66(FJ) [DX1045]
BR93A66(RFJ) [DX1045]
BR93A76(FJ) [DX1045]
BR93A76(RFJ) [DX1045]
BR93A86(FJ) [DX1045]
BR93A86(RFJ) [DX1045]
BR93C46(F) [DX1045]
BR93C46(FV) [DX1059]
BR93C46(RFJ) [DX1045]
BR93C56(F) [DX1045]
BR93C56(FV) [DX1059]
BR93C56(RFJ) [DX1045]
BR93C66(F) [DX1045]
BR93C66(FV) [DX1059]
BR93C66(RFJ) [DX1045]
BR93H46(RFJ) [DX1044]
BR93H56(RFJ) [DX1044]
BR93H66(RFJ) [DX1044]
BR93H76(RFJ) [DX1044]
BR93H86(RFJ) [DX1044]
BR93L46(F) [DX1045]
BR93L46(FV) [DX1059]
BR93L46(RFJ) [DX1045]
BR93L56(F) [DX1045]
BR93L56(FV) [DX1059]
BR93L56(RFJ) [DX1045]
BR93L66(F) [DX1045]
BR93L66(FV) [DX1059]
BR93L66(RFJ) [DX1045]
BR93L76(FJ) [DX1045]
BR93L76(RFJ) [DX1045]
BR93L76(RFVJ) [DX1015]
BR9016(RFV) [DX1059]
BR9016A(RFV) [DX1059]
BR9020 [DX0001]
BR9020(FV) [DX1059]
BR9020(RFVM) [DX1015]
BR9040(F) [DX1045]
BR9040(RFV) [DX1059]
BR9080 [DX0001]
BR9080(RFV) [DX1059]
BR9080A(F) [DX1045]
BR9080A(RFV) [DX1059]
BR93A46(F) [DX1045]
BR93A46(RF) [DX1045]
BR93A56(F) [DX1045]
BR93A56(RF) [DX1045]
BR93A66(F) [DX1045]
BR93A66(RF) [DX1045]
BR93A76(F) [DX1045]
BR93A76(RF) [DX1045]
BR93A86(F) [DX1045]
BR93A86(RF) [DX1045]
BR93C46 [DX0001]
BR93C46(FJ) [DX1045]
BR93C46(RF) [DX1045]
BR93C56 [DX0001]
BR93C56(FJ) [DX1045]
BR93C56(RF) [DX1045]
BR93C66 [DX0001]
BR93C66(FJ) [DX1045]
BR93C66(RF) [DX1045]
BR93H46(RF) [DX1044]
BR93H56(RF) [DX1044]
BR93H66(RF) [DX1044]
BR93H76(RF) [DX1044]
BR93H86(RF) [DX1044]
BR93L46 [DX0001]
BR93L46(FJ) [DX1045]
BR93L46(RF) [DX1045]
BR93L56 [DX0001]
BR93L56(FJ) [DX1045]
BR93L56(RF) [DX1045]
BR93L66 [DX0001]
BR93L66(FJ) [DX1045]
BR93L66(RF) [DX1045]
BR93L76(F) [DX1045]
BR93L76(RF) [DX1045]
BR93L76(RFV) [DX1059]
BR93L76(RFVM) [DX1015]

BR93L76(RFVT) [DX1059]
BR93L86(F) [DX1045]
BR93L86(FJ) [DX1045]
BR93L86(RF) [DX1045]
BR93L86(RFJ) [DX1045]
BR93L86(RFV) [DX1059]
BR93L86(RFVJ) [DX1015]
BR93L86(RFVM) [DX1015]
BR93L86(RFVT) [DX1059]
BR93LC46 [DX0001]
BR93LC46(F) [DX1045]
BR93LC46(FJ) [DX1045]
BR93LC46(FV) [DX1059]
BR93LC46(RF) [DX1045]
BR93LC46(RFJ) [DX1045]
BR93LC56 [DX0001]
BR93LC56(F) [DX1045]
BR93LC56(FJ) [DX1045]
BR93LC56(FV) [DX1059]
BR93LC56(RF) [DX1045]
BR93LC56(RFJ) [DX1045]
BR93LC66 [DX0001]
BR93LC66(F) [DX1045]
BR93LC66(FJ) [DX1045]
BR93LC66(FV) [DX1059]
BR93LC66(RF) [DX1045]
BR93LC66(RFJ) [DX1045]
BR93LL46(F) [DX1045]
BR93LL46(FV) [DX1059]
BR95010@SOP8 [DX1045]
BR95010@TSSOP8 [DX1059]
BR95010@TSSOP8(3*3) [DX1015]
BR95020@SOP8 [DX1045]
BR95020@TSSOP8 [DX1059]
BR95020@TSSOP8(3*3) [DX1015]
BR95040@SOP8 [DX1045]
BR95040@TSSOP8 [DX1059]
BR95040@TSSOP8(3*3) [DX1015]
BR95080@SOP8 [DX1045]
BR95080@TSSOP8 [DX1059]
BR95160@SOP8 [DX1045]
BR95160@TSSOP8 [DX1059]
BR9877FV [DX1059]
BRCA016GWZ-W [DX0001]
BU9829GUL-W [DX0001]
BU9832GUL-W [DX0001]
BU9833GUL-W [DX0001]
BU9844GUL-W [DX0001]
BU9847GUL-W [DX0001]
BU9880GUL-W [DX0001]
BU9888FV-W [DX1059]
BU9889GUL-W [DX0001]
BU9890GUL-W [DX0001]
BU9891GUL-W [DX0001]
BU9897GUL-W [DX0001]
BU99901GUZ-W [DX0001]

SAIFUN

E(E)PROM/FRAM/NVRAM

SA24C1024 [DX0001]
SA24C1024@SOIC8 [DX1045]
SA24C512 [DX0001]
SA24C512@SOIC8 [DX1045]
SA24C512@TSSOP8 [DX1059]
SA25C020 [DX0001]
SA25C020@MLF8 [DX4005#1]
SA25C020@SOIC8 [DX1045#1]
SA25C040 [DX0001]
SA25C040@MLF8 [DX4005#1]
SA25C040@SOIC8 [DX1045#1]
SA25C080 [DX0001]
SA25C080@MLF8 [DX4005#1]
SA25C080@SOIC8 [DX1045#1]
SA25C1024(H) [DX0001]
SA25C1024(H)@CSP8 [DX4005]
SA25C1024(H)@SOIC8 [DX1045]
SA25C1024(L) [DX0001]
SA25C1024(L)@CSP8 [DX4005]
SA25C1024(L)@SOIC8 [DX1045]
SA25C512(H)
SA25C512(H)@CSP8 [DX4005]
SA25C512(H)@SOIC8 [DX1045]
SA25C512(L) [DX0001]
SA25C512(L)@CSP8 [DX4005]
SA25C512(L)@SOIC8 [DX1045]
SA25F005 [DX0001]
SA25F005@MLF8 [DX4005]

SA25F005@SOIC8 [DX1045]
SA25F010 [DX0001]
SA25F010@MLF8 [DX4005]
SA25F010@SOIC8 [DX1045]
SA25F020 [DX0001]
SA25F020@MLF8 [DX4005#1]
SA25F020@SOIC8 [DX1045#1]
SA25F040 [DX0001]
SA25F040@MLF8 [DX4005#1]
SA25F040@SOIC8 [DX1045#1]
SA25F080 [DX0001]
SA25F080@MLF8 [DX4005#1]
SA25F080@SOIC8 [DX1045#1]
SA25F160 [DX0001]
SA25F160(ISP) [DX0001]
SA25F160@MLF8 [DX4005#1]
SA25F160@MLF8(ISP) [DX0001]
SA25F160@SOIC16 [DX1030]
SA25F160@SOIC16(ISP) [DX0001]

SAMSUNG

E(E)PROM/FRAM/NVRAM

K511F12ACM@FBGA107 [DX5028]
K511F13ACA@FBGA137 [DX5011]
K511F13ACC@FBGA130 [DX5140]
K511F57ACB@FBGA107 [DX5028]
K511F57ACC@FBGA107 [DX5028]
K511F58ACA@FBGA137 [DX5011]
K511F58ACB@FBGA137 [DX5011]
K511F58ACC@FBGA137 [DX5011]
K511F58ACM@FBGA137 [DX5011]
K512H1GACC@FBGA137 [DX5011]
K512H1HACM@FBGA107 [DX5028]
K521F12ACB@FBGA107 [DX5028]
K521F12ACD@FBGA107 [DX5028]
K521F13ACA@FBGA137 [DX5011]
K521F13ACM@FBGA137 [DX5011-1]
K521F57ACA@FBGA107 [DX5028]
K521F57ACM@FBGA107 [DX5028]
K521H12ACB@FBGA107 [DX5028]
K521H12ACC@FBGA130 [DX5140-1]
K521H12ACJ@FBGA107 [DX5028-1]
K521H12ACM@FBGA107 [DX5028]
K521H1HACA@FBGA130 [DX5028]
K521H57ACA@FBGA130 [DX5140-1]
K521H57ACB@FBGA107 [DX5028]
K521H57ACD@FBGA130 [DX5140-1]
K521H57ACM@FBGA107 [DX5028]
K522F1GACA@FBGA137 [DX5011]
K522F1GACM@FBGA137 [DX5010]
K522H1HACA@FBGA107 [DX5028]
K522H1HACC@FBGA153 [DX5165]
K522H1HACD@FBGA107 [DX5028]
K522H1HACM@FBGA107 [DX5028]
K522H2GACM@FBGA137 [DX5011-1]
K524G2GACB@FBGA137 [DX5011-1]
K524G2GACD@BGA137 [DX5011-1]
K524G2GACF@BGA137 [DX5011-1]
K524G2GACH@FBGA137 [DX5011-1]
K524G2GACI@FBGA137 [DX5011-1]
K5A3240CBM@FBGA69 [DX5001]
K5A3240CTM@FBGA69 [DX5001]
K5A3240YBB@FBGA69 [DX5001]
K5A3240YBC@FBGA69 [DX5001]
K5A3240YBM@FBGA69 [DX5001]
K5A3240YTB@FBGA69 [DX5001]
K5A3240YTC@FBGA69 [DX5001]
K5A3240YTM@FBGA69 [DX5001]
K5A3280YBA@FBGA69 [DX5001]
K5A3280YBB@FBGA69 [DX5001]
K5A3280YBC@FBGA69 [DX5001]
K5A3280YBM@FBGA69 [DX5001]
K5A3280YTA@FBGA69 [DX5001]
K5A3280YTB@FBGA69 [DX5001]
K5A3280YTC@FBGA69 [DX5001]
K5A3280YTM@FBGA69 [DX5001]
K5A3281CBM@FBGA69 [DX5001]
K5A3281CTM@FBGA69 [DX5001]
K5A3340YBB@FBGA69 [DX5001]
K5A3340YBC@FBGA69 [DX5001]
K5A3340YTB@FBGA69 [DX5001]
K5A3340YTC@FBGA69 [DX5001]
K5A3380YBB@FBGA69 [DX5001]
K5A3380YBC@FBGA69 [DX5001]
K5A3380YTB@FBGA69 [DX5001]
K5A3380YTC@FBGA69 [DX5001]

K5A6317CBM@FBGA69 [DX5001]
K5A6317CTM@FBGA69 [DX5001]
K5D1213ACE@FBGA137 [DX5011]
K5D1213ACJ@FBGA137 [DX5011]
K5D1213ACM@FBGA137 [DX5011]
K5D12571CM@FBGA107 [DX5028]
K5D1257ACB@FBGA107 [DX5028]
K5D1257ACC(XY)@FBGA107 [DX5028]
K5D1257ACC@FBGA107 [DX5028]
K5D1257ACF@FBGA107 [DX5028]
K5D1257ACM@FBGA107 [DX5028]
K5D1257DCA@FBGA107 [DX5028]
K5D1257DCM@FBGA107 [DX5028]
K5D1258ACA@FBGA120 [DX5116]
K5D1258ACB@FBGA137 [DX5011]
K5D1258ACC@FBGA130 [DX5140]
K5D1258ACM@FBGA137 [DX5011]
K5D1258DCA@FBGA137 [DX5011]
K5D1258DCB@FBGA137 [DX5011]
K5D1258DCM@FBGA137 [DX5011]
K5D1G12ACA@FBGA152 [DX5137]
K5D1G12ACB@FBGA107 [DX5028]
K5D1G12ACD(XSR)@FBGA107 [DX5028]
K5D1G12ACD@FBGA107 [DX5028]
K5D1G12ACE@FBGA107 [DX5028]
K5D1G12ACK(XSR)@FBGA107 [DX5028]
K5D1G12ACK@FBGA107 [DX5028]
K5D1G12DCA@FBGA107 [DX5028]
K5D1G12DCM@FBGA107 [DX5028]
K5D1G13ACD@FBGA137 [DX5011]
K5D1G13ACH@FBGA137 [DX5011]
K5D1G13ACJ@FBGA137 [DX5011-1]
K5D1G13DCA@FBGA137 [DX5011]
K5D1G13DCM@FBGA137 [DX5011]
K5D1G1GACA@FBGA137 [DX5011]
K5D1G58ACA@FBGA137 [DX5011]
K5D1G58ACB@FBGA137 [DX5011]
K5D1H12ACC@FBGA107 [DX5028]
K5D5613HCM@FBGA137 [DX5011]
K5D5613VCM@FBGA137 [DX5011]
K5D5657ACA@FBGA107 [DX5028]
K5D5657ACB@FBGA107 [DX5028]
K5D5657ACC@FBGA107 [DX5028]
K5D5657DCA@FBGA107 [DX5028]
K5E1212ACJ@FBGA107 [DX5028]
K5E1213ACC@FBGA130 [DX5140]
K5E1257ACM@FBGA107 [DX5028]
K5E1G12ACC@FBGA107 [DX5028]
K5E1G12ACG@FBGA107 [DX5028]
K5E1G13ACA@FBGA137 [DX5012]
K5E1G13ACM@FBGA137 [DX5012]
K5E1G58ACM@FBGA137 [DX5011]
K5E1H12ACB@FBGA107 [DX5028]
K5E1H12ACM@FBGA107 [DX5028]
K5E1H57ACM@FBGA107 [DX5028]
K5E2G1GACM@FBGA137 [DX5010]
K5G2829ATM@FBGA132 [DX5069]
K5J6316CBM@FBGA69 [DX5001]
K5J6316CTM@FBGA69 [DX5001]
K5J6332CBM@FBGA69 [DX5001]
K5J6332CTM@FBGA69 [DX5001]
K5L2731CAA@FBGA64 [DX5001]
K5L2731CAM@FBGA64 [DX5001]
K5L2763CAA@FBGA64 [DX5001]
K5L2763CAM@FBGA64 [DX5001]
K5L2833ABA@FBGA84 [DX5001]
K5L2833ABM@FBGA84 [DX5001]
K5L2833ATA@FBGA84 [DX5001]
K5L2833ATM@FBGA84 [DX5001]
K5L2864ABM@FBGA115 [DX5057]
K5L2864ATM@FBGA115 [DX5057]
K5L2866ABA@FBGA84 [DX5001]
K5L2866ABB@FBGA84 [DX5001]
K5L2866ABC@FBGA84 [DX5001]
K5L2866ABD@FBGA84 [DX5001]
K5L2866ATA@FBGA84 [DX5001]
K5L2866ATB@FBGA84 [DX5001]
K5L2866ATC@FBGA84 [DX5001]
K5L2866ATD@FBGA84 [DX5001]
K5L2931CAM@FBGA64 [DX5001]
K5L3216CAM@FBGA69 [DX5001]
K5L3316CAM@FBGA69 [DX5001]
K5L5563CAA@FBGA84 [DX5001]
K5L5666ABA@FBGA84 [DX5001]
K5L5666ABB@FBGA84 [DX5001]
K5L5666ATA@FBGA84 [DX5001]
K5L5666ATB@FBGA84 [DX5001]
K5L6331CAA@FBGA56 [DX5045]
K5L6331CAM@FBGA56 [DX5045]
K5L6363CAM@FBGA56 [DX5045]
K5L6531CAM@FBGA56 [DX5045]
K5L6532ABA@FBGA115 [DX5084]
K5L6532ATA@FBGA115 [DX5084]
K5L6563CAM@FBGA56 [DX5045]
K5L6631CAA@FBGA56 [DX5045]
K5N2833ABB@FBGA56 [DX5135]

K5N2833ABM@FBGA56 [DX5066]
K5N2833ATB@FBGA56 [DX5135]
K5N2833ATM@FBGA56 [DX5066]
K5N2866ABB@FBGA56 [DX5135]
K5N2866ABE@FBGA56 [DX5135]
K5N2866ATB@FBGA56 [DX5135]
K5N2866ATE@FBGA56 [DX5135]
K5N2866ATM@FBGA56 [DX5066]
K5N3217ABM@FBGA56 [DX5066]
K5N3217ATM@FBGA56 [DX5066]
K5N5629ABB@FBGA56 [DX5066]
K5N5629ABM@FBGA56 [DX5066]
K5N5629ATB@FBGA56 [DX5066]
K5N5629ATM@FBGA56 [DX5066]
K5N5666ABD@FBGA56 [DX5066]
K5N5666ATD@FBGA56 [DX5066]
K5N6433ABM@FBGA52 [DX5135]
K5N6433ATM@FBGA52 [DX5135]
K5R1213ACA@FBGA202 [DX5138]
K5R1G13ACM-DJ90@FBGA167 [DX5097]
K5W1G12ACA-DK75@FBGA167 [DX5097]
K8D1616UBA@TSOP48 [DX1004]
K8D1716UBA@TSOP48 [DX1004]
K8D1716UBC@TSOP48 [DX1004]
K8D1716UTC@FBGA48 [DX5039]
K8D3216UBB@FBGA48 [DX5039]
K8D3216UBC@FBGA48 [DX5039]
K8D3216UBM@TSOP48 [DX1004]
K8D3216UTB@TSOP48 [DX1004]
K8D3216UTC@TSOP48 [DX1004]
K8D3216UTM@TSOP48(new) [DX1004]
K8D3316UBC@TSOP48 [DX1004]
K8D3316UTC@FBGA48 [DX5039]
K8D3316UTM@TSOP48 [DX1004]
K8D6316UBM@TSOP48 [DX1004]
K8D6316UTM@TSOP48 [DX1004]
K8P2815UQB@FBGA64 [DX5074]
K8P2815UQC@FBGA80 [DX5001]
K8P3215UQB@FBGA64 [DX5074]
K8P5516UZB@FBGA64 [DX5074]
K8P5615UQA@FBGA83 [DX5001]
K8P6415UQB@FBGA48 [DX5002]
K8P6415UQB@TSOP48 [DX1004]
K8S3015EBF@FBGA44 [DX5099]
K8S3215EBF@FBGA44 [DX5177]
K9F1208R0C@FBGA63 [DX5062]
K9F1208U0B@TSOP48 [DX1004]
K9F1208U0C@TSOP48 [DX1004]
K5N2833ABM@FBGA84 [DX5001]
K5N2833ATM(YS)@FBGA84 [DX5001]
K5N2833ATM@FBGA84 [DX5001]
K5N2866ABD@FBGA56 [DX5135]
K5N2866ABM@FBGA56 [DX5066]
K5N2866ATD@FBGA56 [DX5135]
K5N2866ATF@FBGA56 [DX5135]
K5N3217ABA@FBGA56 [DX5135]
K5N3217ATA@FBGA56 [DX5135]
K5N5629ABA@FBGA56 [DX5066]
K5N5629ABC@FBGA56 [DX5066]
K5N5629ATA@FBGA56 [DX5066]
K5N5629ATC@FBGA56 [DX5066]
K5N5666ABB@FBGA56 [DX5066]
K5N5666ATB@FBGA56 [DX5066]
K5N6433ABB@FBGA52 [DX5135]
K5N6433ATB@FBGA52 [DX5135]
K5P1H13ACM@FBGA107 [DX5028]
K5R1213ACC@FBGA202 [DX5138]
K5R2G1GACM-DK75@FBGA167 [DX5097]
K7A403600A@TQFP100 [DX3062]
K8D1616UTA@TSOP48 [DX1004]
K8D1716UBC@FBGA48 [DX5039]
K8D1716UTA@TSOP48 [DX1004]
K8D1716UTC@TSOP48 [DX1004]
K8D3216UBB@TSOP48 [DX1004]
K8D3216UBC@TSOP48 [DX1004]
K8D3216UTB@FBGA48 [DX5039]
K8D3216UTC@FBGA48 [DX5039]
K8D3216UTM@TSOP48 [DX1004]
K8D3316UBC@FBGA48 [DX5039]
K8D3316UBM@TSOP48 [DX1004]
K8D3316UTC@TSOP48 [DX1004]
K8D6316UBM@FBGA48 [DX5039]
K8D6316UTM@FBGA48 [DX5039]
K8D6416UM@SSOP56 [DX0051]
K8P2815UQB@FBGA80 [DX5001]
K8P3215UQB@FBGA48 [DX5002]
K8P3215UQB@TSOP48 [DX1004]
K8P5516UZB@TSOP56 [DX1011]
K8P5615UQA@TSOP56 [DX1055]
K8P6415UQB@FBGA64 [DX5074]
K8Q2815UQB@TSOP56 [DX1011]
K8S3015ETF@FBGA44 [DX5099]
K8S3215ETF@FBGA44 [DX5177]
K9F1208U0B@FBGA63 [DX5062]
K9F1208U0C@FBGA63 [DX5062]
K9F1208U0M@TSOP48 [DX1004]

K9F1216U0A@TSOP48 [DX1004]
K9F1G08R0A@FBGA63 [DX5044]
K9F1G08R0B@FBGA63 [DX5046]
K9F1G08U0A@FBGA63 [DX5044]
K9F1G08U0A@TSOP48 [DX1004]
K9F1G08U0B@TSOP48 [DX1004]
K9F1G08U0C@TSOP48 [DX1004-1]
K9F1G08U0D@BGA63 [DX5046]
K9F1G08U0D@TSOP48 [DX1004-3]
K9F1G08U0E@TSOP48 [DX1004-3]
K9F1G08U0M@TSOP48 [DX1004]
K9F1G16U0M@TSOP48 [DX1004]
K9F2808U0B@TSOP48 [DX1004]
K9F2808U0C@TSOP48 [DX1004]
K9F2G08R0A@FBGA63 [DX5168]
K9F2G08U0A@TSOP48 [DX1004]
K9F2G08U0B@TSOP48 [DX1004-1]
K9F2G08U0C@BGA63 [DX5046]
K9F2G08U0C@TSOP48 [DX1004-3]
K9F2G08U0M@TSOP48 [DX1004]
K9F4G08U0A@TSOP48 [DX1004]
K9F4G08U0B@TSOP48 [DX1004-1]
K9F4G08U0D@TSOP48 [DX1004-1]
K9F4G08U0E@TSOP48 [DX1004-3]
K9F4G08U0M@TSOP48 [DX1004]
K9F5608R0D@FBGA63 [DX5046]
K9F5608U0B@TSOP48 [DX1004]
K9F5608U0C@FBGA63 [DX5046]
K9F5608U0C@TSOP48 [DX1004]
K9F5608U0C@WSOP48 [DX1004]
K9F5608U0D@FBGA63 [DX5046]
K9F5608U0D@TSOP48 [DX1004]
K9F5608U0D@WSOP48 [DX1042]
K9F8G08U0M@TSOP48 [DX1004]
K9G4G08U0A@TSOP48 [DX1004]
K9G4G08U0B@TSOP48 [DX1004-3]
K9G8G08U0A@TSOP48 [DX1004-1]
K9G8G08U0B@TSOP48 [DX1004-1]
K9G8G08U0C@TSOP48 [DX1004-1]
K9G8G08U0M@TSOP48 [DX1004]
K9GAG08U0D@TSOP48 [DX1004-1]
K9GAG08U0E@TSOP48 [DX1004]
K9GAG08U0F@TSOP48 [DX1004-3]
K9GAG08U0M@TSOP48 [DX1004-1]
K9GBG08U0A@TSOP48 [DX1004-3]
K9GBG08U0B@TSOP48 [DX1004-3]
K9HBG08U1M(T)@TSOP48 [DX1004]
K9HBG08U1M@TSOP48 [DX1004]
K9HCG08U1M(8G)@TSOP48 [DX1004]
K9HCG08U1M@TSOP48 [DX1004]
K9K1G08U0B@FBGA63 [DX5062]
K9K1G08U0M@TSOP48 [DX1004]
K9K2G08U0M@TSOP48 [DX1004]
K9K4G08U0M@TSOP48 [DX1004]
K9K8G08U0A@TSOP48 [DX1004]
K9K8G08U0B@TSOP48 [DX1004-3]
K9K8G08U0D@TSOP48 [DX1004-1]
K9K8G08U0E@TSOP48 [DX1004-3]
K9K8G08U0M@TSOP48 [DX1004-3]
K9KAG08U0M@TSOP48 [DX1004-1]
K9L8G08U0M@TSOP48 [DX1004]
K9LAG08U0M@TSOP48 [DX1004]
K9LBG08U0D(4G)@TSOP48 [DX1004-1]
K9LBG08U0D@TSOP48 [DX1004-1]
K9LBG08U0M@TSOP48 [DX1004-1]
K9T1G08U0M@TSOP48 [DX1004]
K9WAG08U1A@TSOP48 [DX1004]
K9WAG08U1B@TSOP48 [DX1004-1]
K9WAG08U1M@TSOP48 [DX1004]
K9WBG08U1M@TSOP48 [DX1004-1]
K9WBG08U1M1@TSOP48 [DX1004]
KA100H00DA@FBGA137 [DX5011]
KA1000015B@FBGA137 [DX5011-1]
KA1000015C@FBGA240 [DX5185]
KA1000015D@FBGA153 [DX5198]
KA1000015E@FBGA137 [DX5011]
KA1000015F@FBGA240 [DX5185]
KA1000015M@FBGA137 [DX5011-1]
KAD050300B@TBGA69 [DX5001]
KAD060300B@TBGA69 [DX5001]
KAD060300C@TBGA69 [DX5001]
KAD060700D@TBGA69 [DX5001]
KAD070300B@TBGA69 [DX5001]
KAD070300C@TBGA69 [DX5001]
KAD070700D@TBGA69 [DX5001]
KAD070J00M@TBGA69 [DX5001]
KAD080300B@TBGA69 [DX5001]
KAD090300B@TBGA69 [DX5001]
KAD100300B@TBGA69 [DX5001]
KAG001002M@FBGA137 [DX5012]
KAG00G003A@FBGA107 [DX5028]
KAG00J007M@FBGA107 [DX5028]
KAG00K003M@FBGA107 [DX5028]
KAG00K007A@FBGA107 [DX5028]
KAL009001M@FBGA137 [DX5010]
KAL00E00VC@FBGA137 [DX5010]

KAL000015M@FBGA137 [DX5011-1]
KAL00R00KM@FBGA137 [DX5012]
KAL00T00UM@FBGA137 [DX5012]
KAL00X00UA-DJYY@FBGA137 [DX5011]
KAL00X00UM-DJYY@FBGA137 [DX5011]
KAP17WG00M(Nor)@FBGA167 [DX0001]
KAT00W00EM-DU55@FBGA167 [DX5097]
KAX333700M(NAND)@FBGA137 [DX5012]
KAX333700M(Nor)@FBGA137 [DX5012]
KB1000012M@BGA137 [DX5011-1]
KB1000015B@BGA137 [DX5011-1]
KB1000015M@BGA137 [DX5011-1]
KBE00500AM@FBGA137 [DX5011]
KBE00F003A@FBGA107 [DX5028]
KBE00G005M@FBGA137 [DX5011]
KBE00M005M@FBGA137 [DX5011]
KBE00S009M@FBGA137 [DX5010]
KBE00S00AA@FBGA137 [DX5011]
KBJ10KB00A(OneNAND)@FBGA167 [DX5073]
KBJ17KC00A(OneNAND)@FBGA167 [DX5073]
KBY00N00HA@BGA137 [DX5011-1]
KBY00N00HM@FBGA137 [DX5011]
KBY00U00VA@FBGA137 [DX5011]
KBY00U00VM@FBGA137 [DX5011]
KFG1216Q2B-DEB8@FBGA63 [DX5173]
KFG1216U2A-DIB5@FBGA63 [DX5173]
KFG1216U2A-DIB6@FBGA63 [DX5173]
KFG1216U2B-DIB6@FBGA63 [DX5173]
KFG1G16Q2A@FBGA63 [DX5168]
KFG2G16Q2B@FBGA63 [DX5046]
KFG5616U1A@TSOP48 [DX1004]
KFM2G16Q2B@FBGA63 [DX5046]
KLM2G1HE3F@FBGA153 [DX5104]
KLM4G1FE3B@FBGA153 [DX5104]
KLM4G2DEJE(20M)@BGA169 [DX5113]
KLM4G2DEJE@BGA169 [DX5113]
KLM8G3FE3B(1G)@BGA153 [DX5104]
KLMAG4FEKA@BGA169 [DX5113]
KLMCG8GE4A(20M)@FBGA169 [DX5113]
KLMCG8GE4A@FBGA169 [DX5113]
KM2816A [DX0001]
KM2816AI [DX0001]
KM2817A [DX0001]
KM2817AI [DX0001]
KM2864A [DX0001]
KM2864AH [DX0001]
KM2865A [DX0001]
KM2865AH [DX0001]
KM28C16 [DX0001]
KM28C16@PLCC32 [DX2032]
KM28C16I [DX0001]
KM28C16I@PLCC32 [DX2032]
KM28C17 [DX0001]
KM28C17@PLCC32 [DX2032]
KM28C17I [DX0001]
KM28C17I@PLCC32 [DX2032]
KM28C256 [DX0001]
KM28C256@PLCC32 [DX2032]
KM28C256I [DX0001]
KM28C256I@PLCC32 [DX2032]
KM28C64 [DX0001]
KM28C64@PLCC32 [DX2032]
KM28C64A [DX0001]
KM28C64A@PLCC32 [DX2032]
KM28C64B [DX0001]
KM28C64B@PLCC32 [DX2032]
KM28C64I [DX0001]
KM28C64I@PLCC32 [DX2032]
KM28C65 [DX0001]
KM28C65@PLCC32 [DX2032]
KM28C65A [DX0001]
KM28C65A@PLCC32 [DX2032]
KM28C65I [DX0001]
KM28C65I@PLCC32 [DX2032]
KM93C06(08bit) [DX0001]
KM93C06(16bit) [DX0001]
KM93C06(G)(08bit)@SOIC8 [DX1045]
KM93C06(G)(16bit)@SOIC8 [DX1045]
KM93C06(GD)(08bit)@SOIC8 [DX1045]
KM93C06(GD)(16bit)@SOIC8 [DX1045]
KM93C07(08bit) [DX0001]
KM93C07(16bit) [DX0001]
KM93C07(G)(08bit)@SOIC8 [DX1045]
KM93C07(G)(16bit)@SOIC8 [DX1045]
KM93C07(GD)(08bit)@SOIC8 [DX1045]
KM93C07(GD)(16bit)@SOIC8 [DX1045]
KM93C46V [DX0001]
KM93C46V(G)@SOIC8 [DX1045]

KM93C46V(GD)@SOIC8 [DX1045]
KM93C47V [DX0001]
KM93C47V(G)@SOIC8 [DX1045]
KM93C47V(GD)@SOIC8 [DX1045]
KM93C56V [DX0001]
KM93C56V(G)@SOIC8 [DX1045]
KM93C56V(GD)@SOIC8 [DX1045]
KM93C57V [DX0001]
KM93C57V(G)@SOIC8 [DX1045]
KM93C57V(GD)@SOIC8 [DX1045]
KM93C66V [DX0001]
KM93C66V(G)@SOIC8 [DX1045]
KM93C66V(GD)@SOIC8 [DX1045]
KM93C67V [DX0001]
KM93C67V(G)@SOIC8 [DX1045]
KM93C67V(GD)@SOIC8 [DX1045]
KMAKG0000M@FBGA169 [DX5151-1]
KMJJS000WM@FBGA153 [DX5104]
KMSJS000KM(P)@FBGA153 [DX5104]
KMSJS000KM@FBGA153 [DX5104]
KMV3U000LM@FBGA169 [DX5113]
KMVIS000LM@FBGA169 [DX5113]
KMVTU000LM@FBGA153 [DX5104]
KS24C010 [DX0001]
KS24C010@SOIC8 [DX1045]
KS24C010@TSSOP8 [DX1059]
KS24C011 [DX0001]
KS24C011@SOIC8 [DX1045]
KS24C011@TSSOP8 [DX1059]
KS24C020 [DX0001]
KS24C020@SOIC8 [DX1045]
KS24C020@TSSOP8 [DX1059]
KS24C021 [DX0001]
KS24C021@SOIC8 [DX1045]
KS24C021@TSSOP8 [DX1059]
KS24C040 [DX0001]
KS24C040@SOIC8 [DX1045]
KS24C040@TSSOP8 [DX1059]
KS24C041 [DX0001]
KS24C041@SOIC8 [DX1045]
KS24C041@TSSOP8 [DX1059]
KS24C080 [DX0001]
KS24C080@SOIC8 [DX1045]
KS24C080@TSSOP8 [DX1059]
KS24C081 [DX0001]
KS24C081@SOIC8 [DX1045]
KS24C081@TSSOP8 [DX1059]
NAND1GTHW@BGA202 [DX5138]
S524A40X10 [DX0001]
S524A40X10@SOP8 [DX1045]
S524A40X10@TSSOP8 [DX1059]
S524A40X11 [DX0001]
S524A40X11@SOP8 [DX1045]
S524A40X11@TSSOP8 [DX1059]
S524A40X20 [DX0001]
S524A40X20@SOP8 [DX1045]
S524A40X20@TSSOP8 [DX1059]
S524A40X21 [DX0001]
S524A40X21@SOP8 [DX1045]
S524A40X21@TSSOP8 [DX1059]
S524A40X40 [DX0001]
S524A40X40@SOP8 [DX1045]
S524A40X40@TSSOP8 [DX1059]
S524A40X41 [DX0001]
S524A40X41@SOP8 [DX1045]
S524A40X41@TSSOP8 [DX1059]
S524A60X51 [DX0001]
S524A60X51@SOP8 [DX1045]
S524A60X51@TSSOP8 [DX1059]
S524A60X81 [DX0001]
S524A60X81@SOP8 [DX1045]
S524A60X81@TSSOP8 [DX1059]
S524AB0X91 [DX0001]
S524AB0X91@SOP8 [DX1045]
S524AB0X91@TSSOP8 [DX1059]
S524AB0XB1 [DX0001]
S524AB0XB1@SOP8 [DX1045]
S524AB0XB1@TSSOP8 [DX1059]
S524AD0XD1 [DX0001]
S524AD0XD1@SOP8 [DX1045]
S524AD0XD1@TSSOP8 [DX1059]
S524AD0XF1 [DX0001]
S524AD0XF1@SOP8 [DX1045]
S524AD0XF1@TSSOP8 [DX1059]
S524C20D11 [DX0001]
S524C20D11@SOP8 [DX1045]
S524C20D11@TSSOP8 [DX1059]
S524C20D21 [DX0001]
S524C20D21@SOP8 [DX1045]
S524C20D21@TSSOP8 [DX1059]
S524C80D41 [DX0001]
S524C80D41@SOP8 [DX1045]
S524C80D41@TSSOP8 [DX1059]
S524C80D81 [DX0001]
S524C80D81@SOP8 [DX1045]
S524C80D81@TSSOP8 [DX1059]

S524L50X51 [DX0001]
S524L50X51@SOP8 [DX1045]
S524L50X51@TSSOP8 [DX1059]
S524LB0X91 [DX0001]
S524LB0X91@SOP8 [DX1045]
S524LB0X91@TSSOP8 [DX1059]
S524LB0XB1 [DX0001]
S524LB0XB1@SOP8 [DX1045]
S524LB0XB1@TSSOP8 [DX1059]
SC32442BH(NAND2G)@FBGA332 [DX5119]
SC32442BL(NAND1G)@FBGA332 [DX5119]

DRAM & SRAM

KM62256A [DX0001]
KM62256A@SOIC28 [DX1035]
KM62256AL [DX0001]
KM62256AL@SOIC28 [DX1035]
KM6264A [DX0001]
KM6264A@SOIC28 [DX1035]
KM6264AL [DX0001]
KM6264AL@SOIC28 [DX1035]
KM68257LP [DX0001]
KM68257LP@SOIC28 [DX1035]
KM68257P [DX0001]
KM68257P@SOIC28 [DX1035]
KM6865LP [DX0001]
KM6865LP@SOIC28 [DX1035]
KM6865P [DX0001]
KM6865P@SOIC28 [DX1035]

PLD

CPL16L8 [DX0001]
CPL16L8@PLCC20 [DX2020]
CPL16L8L [DX0001]
CPL16L8L@PLCC20 [DX2020]
CPL16R4 [DX0001]
CPL16R4@PLCC20 [DX2020]
CPL16R4L [DX0001]
CPL16R4L@PLCC20 [DX2020]
CPL16R6 [DX0001]
CPL16R6@PLCC20 [DX2020]
CPL16R6L [DX0001]
CPL16R6L@PLCC20 [DX2020]
CPL16R8 [DX0001]
CPL16R8@PLCC20 [DX2020]
CPL16R8L [DX0001]
CPL16R8L@PLCC20 [DX2020]

MICROCONTROLLER

HARTI910@PQFP64 [DX3064]
HARTM310@MQFO100 [DX3077A]
HZN8275E@LQFP48 [DX3007]
S3F441FX@QFP64 [DX3011]
S3F80P5@QFN24 [DX4012]
S3F80P5@SOP24 [DX1033]
S3F80PB@QFN32 [DX4015]
S3F80PB@QFN44 [DX4018]
S3F80PB@QFP44 [DX3046]
S3F80PB@SOP32 [DX1035]
S3F80Q5@QFN24 [DX4012]
S3F80QB@QFN44 [DX4018]
S3F80QB@QFP44 [DX3046]
S3F8235@PQFP64 [DX3015]
S3F8235@QFP64 [DX3011]
S3F8235@SDIP64 [DX0064]
S3F8274@QFP48 [DX3007]
S3F8275@PQFP64 [DX3015]
S3F8275@QFP64 [DX3011]
S3F8285@PQFP80 [DX3019]
S3F8285@QFP80 [DX3016]
S3F84B8@DIP20
S3F84B8@SOP20 [DX1033]
S3F84I8@QFP44 [DX3046]
S3F84I8@SDIP42 [DX0042]
S3F84I9@QFP44 [DX3046]
S3F84I9@SDIP42 [DX0042]
S3F84K4@DIP16

S3F84K4@DIP20
S3F84K4@SOP16 [DX1033]
S3F84K4@SOP20 [DX1033]
S3F84K4@SSOP20 [DX1000]
S3F84NB@PQFP64 [DX3015]
S3F84NB@SDIP64 [DX0064]
S3F84P4
S3F84P4@SOP8 [DX1030]
S3F84U8@QFP44 [DX3046]
S3F84U8@SDIP42 [DX0042]
S3F84UA@QFP44 [DX3046]
S3F84UA@SDIP42 [DX0042]
S3F84VB@PQFP64 [DX3015]
S3F84VB@SDIP64 [DX0064]
S3F8S15@LQFP48 [DX3007]
S3F8S15@QFP48 [DX3123]
S3F8S18@LQFP48 [DX3007]
S3F8S18@QFP48 [DX3123]
S3F8S19@LQFP48 [DX3007]
S3F8S19@QFP48 [DX3123]
S3F8S24@DIP20
S3F8S24@DIP24
S3F8S24@SOP20 [DX1033]
S3F8S24@SOP24 [DX1033]
S3F8S24@SSOP20 [DX1001]
S3F8S28@DIP20
S3F8S28@DIP24
S3F8S28@SOP20 [DX1033]
S3F8S28@SOP24 [DX1033]
S3F8S28@SSOP20 [DX1001]
S3F8S34@SDIP32 [DX0032]
S3F8S34@SOP32 [DX1035]
S3F8S35@SDIP32 [DX0032]
S3F8S35@SOP32 [DX1035]
S3F8S38@SDIP32 [DX0032]
S3F8S38@SOP32 [DX1035]
S3F8S39@SDIP32 [DX0032]
S3F8S39@SOP32 [DX1035]
S3F8S45@QFP44 [DX3046]
S3F8S45@SDIP32 [DX0032]
S3F8S45@SDIP42 [DX0042]
S3F8S5A@QFP44 [DX3046]
S3F8S5A@SDIP42 [DX0042]
S3F8S6B@PQFP64 [DX3015]
S3F8S6B@QFP64 [DX3011]
S3F8S6B@SDIP64 [DX0064]
S3F8S7B@PQFP80 [DX3019]
S3F8S7B@QFP80 [DX3016]
S3F8S8B@PQFP100 [DX3022]
S3F8S8B@QFP100 [DX3021]
S3F9444
S3F9444@SOP8 [DX1030]
S3F9454(dip16)
S3F9454(dip20)
S3F9454@SOP20 [DX1033]
S3F9454@SSOP20 [DX1001]
S3F9488@QFP44 [DX3046]
S3F9488@SDIP32 [DX0032]
S3F9488@SDIP42 [DX0042]
S3F9488@SOP32 [DX1035]
S3F9498@SDIP30 [DX0032]
S3F9498@SDIP32 [DX0032]
S3F9498@SOP28 [DX1033]
S3F9498@SOP32 [DX1035]
S3F94A5@QFP44 [DX3046]
S3F94A5@SDIP32 [DX0032]
S3F94A5@SDIP42 [DX0042]
S3F94C4@DIP20
S3F94C4@SOP20 [DX1033]
S3F94C8@DIP20
S3F94C8@SOP20 [DX1033]
S3FC40D@QFP128 [DX3033]
S3P414@QFP44 [DX3046]
S3P434@QFP44 [DX3046]
S3P7048@QFP44 [DX3046]
S3P7048@SDIP42 [DX0042]
S3P70F4@SDIP30 [DX0032]
S3P70F4@SOP32 [DX1035]
S3P7224@PQFP64 [DX3015]
S3P7235@PQFP80 [DX3019]
S3P7238@PQFP80 [DX3019]
S3P72B9@PQFP128 [DX3032]
S3P72F5@PQFP100 [DX3023]
S3P72K8@PQFP80 [DX3019]
S3P72M9@PQFP128 [DX3032]
S3P72N5@PQFP80 [DX3019]
S3P72N8@PQFP80 [DX3019]
S3P72P9@PQFP100 [DX3023]
S3P72Q5@PQFP100 [DX3023]
S3P7335@PQFP80 [DX3019]
S3P7414@SDIP42 [DX0042]
S3P7424@SDIP30 [DX0032]
S3P7424@SOP28 [DX1033]
S3P7434@SDIP42 [DX0042]
S3P7515@PQFP64 [DX3015]
S3P7515@SDIP64 [DX0064]

S3P7528@QFP44 [DX3046]
S3P7528@SDIP42 [DX0042]
S3P7538@SDIP30 [DX0032]
S3P7538@SOP32 [DX1035]
S3P7565@PQFP100 [DX3023]
S3P8245@PQFP80 [DX3019]
S3P8245@QFP80 [DX3016]
S3P8249@PQFP80 [DX3019]
S3P8249@QFP80 [DX3016]
S3P8469@PQFP64 [DX3015]
S3P8469@SDIP64 [DX0064]
S3P8475@SDIP42 [DX0042]
S3P8475@TQFP44 [DX3046]
S3P848A@PQFP64 [DX3015]
S3P848A@SDIP64 [DX0064]
S3P9228@QFP44 [DX3046]
S3P9228@SDIP42 [DX0042]
S3P9234@PQFP64 [DX3015]
S3P9234@QFP64 [DX3011]
S3P9428@SDIP30 [DX0032]
S3P9428@SOP28 [DX1033]
S3P9428@SOP32 [DX1035]
S3P9434(dip16)
S3P9434(dip18)
S3P9434(dip20)
S3P9434@SOP20 [DX1033]
SA2DM01X [DX4043]

SAMSUNG-CUSTOMER

E(E)PROM/FRAM/NVRAM

K511F57ACC(ZTE)@FBGA107 [DX5028]
K511F58ACA(GUANGHONG)@FBGA137 [DX5011]
K511F58ACA(XSR10)@FBGA137 [DX5011]
K511F58ACM(NEW)@FBGA137 [DX5011]
K512H1HACM(LG)@FBGA107 [DX5028]
K512H1HACM(ZTE)@FBGA107 [DX5028]
K521F13ACA(XY)@FBGA137 [DX5011]
K521F57ACM(LQ)@FBGA107 [DX5028]
K521H12ACB(YH)@FBGA107 [DX5028]
K521H12ACC(XSR1.0)@FBGA130 [DX5140]
K521H57ACA(XSR1.0)@FBGA130 [DX5140]
K522F1GACM(MTK)@FBGA137 [DX5010]
K522H1HACA(GUANGHONG)@FBGA107 [DX5028]
K522H1HACD(K-Touch)@FBGA107 [DX5028]
K524G2GACB(MTK)@FBGA137 [DX5011]
K5D1213ACE(DATACODE)@FBGA137 [DX5011]
K5D1258ACC@FBGA130 [DX5130]
K5D1258DCA(XY)@FBGA137 [DX5011]
K5D1H12ACC(LG)@FBGA107 [DX5028]
K5D5657DCA(DATACODE)@FBGA107 [DX5028]
K9F1208U0B(KT)@TSOP48 [DX1004]
K9F1208U0C(KT)@TSOP48 [DX1004]
K9F1G08U0A(AMLOGIC)@TSOP48 [DX1004]
K9F1G08U0B(3D)@TSOP48 [DX1004]
K9F1G08U0B(AMLOGIC)@TSOP48 [DX1004-1]
K9F1G08U0B(DJT)@TSOP48 [DX1004]
K9F1G08U0B(HD)@TSOP48 [DX1004]
K9F1G08U0B(KT)@TSOP48 [DX1004]
K9F1G08U0B(M310)@TSOP48 [DX1004]
K9F1G08U0B(SYHD)@TSOP48 [DX1004-3]
K9F1G08U0B@TSOP48(ALI) [DX1004]
K9F1G08U0C(CHUANGJ)@TSOP48 [DX1004-3]
K9F1G08U0C(INSPUR)@TSOP48 [DX1004]
K9F1G08U0C(JiuZhou)@TSOP48 [DX1004-1]
K9F1G08U0C(MLT-XY)@TSOP48 [DX1004-1]

K9F1G08U0C(ST273)@TSOP48 [DX1004-3]
K9F1G08U0C(TRIDENT)@TSOP48 [DX1004-1]
K9F1G08U0D(CHUANGJ)@TSOP48 [DX1004-3]
K9F1G08U0D(MSTAR)@TSOP48 [DX1004-1]
K9F1G08U0D(OMRON)@TSOP48 [DX1004-1]
K9F1G08U0D(RBA)@TSOP48 [DX1004-3]
K9F1G08U0D(REALTEK)@TSOP48 [DX1004-1]
K9F1G08U0D(ST7162)@TSOP48 [DX1004]
K9F1G08U0D(TRIDENT)@TSOP48 [DX1004-1]
K9F1G08U0D(YINGH)@TSOP48 [DX1004]
K9F1G08U0D@TSOP48(ALI) [DX1004]
K9F1G08U0D@TSOP48(DaXian) [DX1004-1]
K9F2G08U0A(RUIKE)@TSOP48 [DX1004]
K9F2G08U0A(UT)@TSOP48 [DX1004]　　K9F2G08U0A(XY)@TSOP48 [DX1004]
K9F2G08U0B(FOXCONN)@TSOP48 [DX1004-1]
K9F2G08U0B(RTK)@TSOP48 [DX1004]
K9F2G08U0B(RUIKE)@TSOP48 [DX1004-1]
K9F2G08U0B(SINAEN)@TSOP48 [DX1004-3]
K9F2G08U0B(UT)@TSOP48 [DX1004-1]
K9F2G08U0B(WISTRON)@TSOP48 [DX1004-1]
K9F2G08U0C(DaXian)@TSOP48 [DX1004-1]
K9F2G08U0C(ST273)@TSOP48 [DX1004-3]
K9F2G08U0C@TSOP48(ChuangJ) [DX1004-3]
K9F2G08U0C@TSOP48(REALTEK) [DX1004-1]
K9F2G08U0C@TSOP48(RUIKE) [DX1004-1]
K9F2G08U0C@TSOP48(ST7142) [DX1004]
K9F2G08U0C@TSOP48(ST7162) [DX1004]
K9F4G08U0A(AMLOGIC)@TSOP48 [DX1004]
K9F4G08U0A(HUAWEI)@TSOP48 [DX1004]
K9F4G08U0A(READ-BAD)@TSOP48 [DX1004-1]
K9F4G08U0B(HUAWEI)@TSOP48 [DX1004]
K9F4G08U0D(BATM)@TSOP48 [DX1004-1]
K9F4G08U0D(REALTEK)@TSOP48 [DX1004-1]
K9F4G08U0D(TRIDENT)@TSOP48 [DX1004-1]
K9F4G08U0D@TSOP48(XY) [DX1004-1]
K9F5608U0D(SUBHA)@TSOP48 [DX1004]
K9F5608U0D(ZTE)@FBGA63 [DX5046]　　K9F5608U0D(ZTE)@TSOP48 [DX1004]
K9F8G08U0M(HD)@TSOP48 [DX1004]
K9G4G08U0A(AMLOGIC)@TSOP48 [DX1004]
K9G8G08U0A(4G)@TSOP48 [DX1004-1]
K9G8G08U0A(ChangHong)@TSOP48 [DX1004-1]
K9G8G08U0M(READ-BAD)@TSOP48 [DX1004-1]
K9GAG08U0F(DIANZ)@TSOP48 [DX1004-3]
K9GAG08U0M(AMLOGIC)@TSOP48 [DX1004]
K9GAG08U0M(HD)@TSOP48 [DX1004-1]　　K9K8G08U0A(SY)@TSOP48 [DX1004]
K9LAG08U0M(2G)@TSOP48 [DX1004]
K9LBG08U0M(Intel)@TSOP48 [DX1004-1]
K9WAG08U1A(HS)@TSOP48 [DX1004]　　K9WAG08U1M(HS)@TSOP48 [DX1004]

KA1000015M(ZTE)@FBGA137 [DX5011]
KA1000015M@FBGA137(INVENTEC) [DX5011]
KLMAG2GE4A(INTEL)(20M)@FBGA169 [DX5158]
KLMAG2GE4A(INTEL)@FBGA169 [DX5158]
KLMBG8FEJA(INTEL)(16G)@FBGA169 [DX5158]
KLMBG8FEJA(INTEL)(20M)@FBGA169 [DX5158]
KLMBG8FEJA(INTEL)(2G)@FBGA169 [DX5158]
KLMCG8GE4A(INTEL)(20M)@FBGA167 [DX5158]
KLMCG8GE4A(INTEL)@FBGA167 [DX5158]
SC32442BH(XY)(NAND2G)@FBGA332 [DX5119]
SC32442BH(XY_SLOW)@FBGA332 [DX5119]
TC58NVG1S3ETA00(ST7162)@TSOP48 [DX1004]

SANDISK

E(E)PROM/FRAM/NVRAM

MD2534-d2G@FBGA115 [DX5057]
SDED5-512M@FBGA115 [DX5057]
SDED7-512M@FBGA115 [DX5095]
SDIN2C2-2G@FBGA169(*) [DX5113]
SDIN2C2-4G(8M)@FBGA169(*) [DX5113]
SDIN2C2-4G@FBGA169(*) [DX5113]
SDIN2C2-8G@FBGA169(*) [DX5113]
SDIN4C2-8G@FBGA169(*) [DX5113]
SDIN5C1-16G@FBGA169(*) [DX5113]
SDIN5C1-4G@FBGA169(*) [DX5113]
SDIN5C1-8G@FBGA169(*) [DX5113]
SDIN5C2-4G@FBGA169(*) [DX5113]
SDIN5C2-8G@FBGA169(*) [DX5113]
SDIN5C4-16G(20M)@FBGA169(*) [DX5113]
SDIN5C4-16G@FBGA169(*) [DX5113]
SDIN5C4-64G(20M)@FBGA169(*) [DX5113]
SDIN5C4-64G@FBGA169(*) [DX5113]
SDIN5D1-2G@FBGA153(*) [DX5104]
SDIN5D1-4G@FBGA153(*) [DX5104]
SDIN5D2-2G@FBGA153(*) [DX5104]
SDIN5D2-4G@FBGA153(*) [DX5104]

SANDISK-CUSTOMER

E(E)PROM/FRAM/NVRAM

SDIN4C2-8G(INTEL)(20M)@FBGA169 [DX5158]
SDIN4C2-8G(INTEL)@FBGA169 [DX5158]
SDIN5C2-4G(INTEL)@FBGA169 [DX1075]
SDIN5C4_16G(INTEL)(16G)@FBGA169 [DX5158]
SDIN5C4-16G(INTEL)(20M)@FBGA169 [DX5158]
SDIN5C4-16G(INTEL)(2G)@FBGA169 [DX5158]
SDIN5C4-32G(INTEL)(20M)@FBGA169 [DX5158]
SDIN5C4-32G(INTEL)(2G)@FBGA169 [DX5158]
SDIN5C4-64G(INTEL)(20M)@FBGA169 [DX5158]
SDIN5C4-64G(INTEL)(2G)@FBGA169 [DX5158]

SANYO

E(E)PROM/FRAM/NVRAM

LE24C041 [DX0001]
LE24C042 [DX0001]
LE24C081 [DX0001]
LE24C082 [DX0001]
LE24C161 [DX0001]
LE24C162 [DX0001]
LE24C322@MFP8 [DX1017]
LE24CB642M [DX1044]
LE24L322@MFP8 [DX1017]
LE25FU106BTT@MSOP8 [DX1017]
LE25FU406BTT@MSOP8 [DX1017]
LE25FW056FN@VSON8 [DX4005#1]
LE25FW106M@SOP8 [DX1045#1]
LE25FW1606FN@VSON8 [DX4005#1]
LE25FW206M@SOP8 [DX1045#1]
LE25FW406BMA@MFP8 [DX1045#1]
LE25FW406M@SOP8 [DX1045#1]
LE25FW806M@SOP8 [DX1045#1]
LE25U40C@SOP8 [DX1045#1]
LE26CW006@WLP6 [DX1041]
LE28C1001AM@SOP32 [DX1020]
LE28C1001ATS@VSOP32 [DX1003]
LE28C1001DTS@VSOP32 [DX1003]
LE28CV1001AT@TSOP32 [DX1002]
LE28CV1001DT@TSOP32 [DX1002]
LE28CW1001DT@TSOP32 [DX1002]
LE28DW1621T@FBGA63 [DX5022]
LE28DW3218AM@PSOP44 [DX1014]
LE28DW8163T@TSOP48 [DX1004]
LE28F1601T(REVERSE)@TSOP40 [DX1005]
LE28F1601T@TSOP40 [DX1005]
LE28F4001ATS@TSOP32 [DX1003]
LE28F8001T(REVERSE)@TSOP40 [DX1005]
LE28F8001T@TSOP40 [DX1005]
LE28FV1101T@TSOP40 [DX1005]
LE28FV1601T(REVERSE)@TSOP40 [DX1005]
LE28FV1601T@TSOP40 [DX1005]
LE28FV4001ATS@TSOP32 [DX1003]
LE28FV4001M@SSOP32 [DX1019]
LE28FV4101T@TSOP48 [DX1004]
LE28FV8001T(REVERSE)@TSOP40 [DX1005]
LE28FV8001T@TSOP40 [DX1005]
LE28FW1633FT@FBGA48 [DX5002]
LE24C041@MFP8 [DX1017]
LE24C042@MFP8 [DX1017]
LE24C081@MFP8 [DX1017]
LE24C082@MFP8 [DX1017]
LE24C161@MFP8 [DX1017]
LE24C162@MFP8 [DX1017]
LE24C322@WLP6 [DX1041]
LE24CB642TT [DX1045]
LE25FU106BMA@MFP8 [DX1017]
LE25FU406BMA@MFP8 [DX1045#1]
LE25FU406C@SOP8 [DX1045#1]
LE25FW056MA@MFP8 [DX1045#1]
LE25FW106T@MSOP8 [DX1017]
LE25FW203ATT@MSOP8 [DX1017]
LE25FW206T@MSOP8 [DX1017]
LE25FW406BTT@MSOP8 [DX1017]
LE25FW406T@MSOP8 [DX1017]
LE25FW806T@MSOP8 [DX1017]
LE25U40C@USON8 [DX4005#1]
LE28BW168T@TSOP48 [DX1008]
LE28C1001AT@TSOP32 [DX1002]
LE28C1001DT@TSOP32 [DX1002]
LE28CV1001AM@SOP32 [DX1020]
LE28CV1001ATS@VSOP32 [DX1003]
LE28CV1001DTS@VSOP32 [DX1003]
LE28CW1001DTS@VSOP32 [DX1003]
LE28DW1621T@TSOP48 [DX1004]
LE28DW8102T@TSOP48 [DX1008]
LE28F1101T@TSOP40 [DX1005]
LE28F2001ATS@TSOP32 [DX1003]
LE28F4001M@SSOP32 [DX1019]
LE28FU4101T@TSOP48 [DX1004]
LE28FV2001ATS@TSOP32 [DX1003]
LE28FV4001CTS@TSOP32 [DX1003]
LE28FV4001T@TSOP32 [DX1003]
LE28FW1633FB@FBGA48 [DX5002]
LE28FW1633TB@TSOP48 [DX1004]

LE28FW1633TT@TSOP48 [DX1004]
LE28FW4101T@TSOP48 [DX1004]
LE28FW8201T@TSOP48 [DX1004]
LE28FW8203TB@FBGA48 [DX5002]
LE28FW8203TB@TSOP48 [DX1004]
LE28FW8203TT@FBGA48 [DX5002]
LE28FW8203TT@TSOP48 [DX1004]

MICROCONTROLLER

LC87F2C64A@QFP80 [DX3018]
LC87F2C64A@TQFP80 [DX3016]
LC87F2G08A [DX1012]
LC87F2J04A@QIP48E [DX3093]
LC87F2J04A@SQFP48 [DX3007]
LC87F2J08A@QIP48E [DX3093]
LC87F2J08A@SQFP48 [DX3007]
LC87F2J16A@QIP48E [DX3093]
LC87F2J16A@SQFP48 [DX3007]
LC87F2J32A@QIP48E [DX3093]
LC87F2J32A@SQFP48 [DX3007]
LC87F5G32A@QIP48E [DX3093]
LC87F5G32A@SQFP48 [DX3007]
LC87F5N62B@QIP100E [DX3022]
LC87F5VP6AU@QIP100E [DX3022]

SCENIX

MICROCONTROLLER

SX20AC/SS/G@SSOP20 [DX1026]
SX20AC/SS@SSOP20 [DX1026]
SX28AC/DP [DX0001]
SX28AC/DP/G [DX0001]
SX28AC/SS/G@SSOP28 [DX1026]
SX28AC/SS@SSOP28 [DX1026]
SX48BD/G@TQFP48 [DX3047]
SX48BD@TQFP48 [DX3047]

SEEQ

E(E)PROM/FRAM/NVRAM

27128 [DX0001]
27256 [DX0001]
2764 [DX0001]
27C256 [DX0001]
2804 [DX0001]
2804A [DX0001]
2816A [DX0001]
2816AH [DX0001]
5213 [DX0001]
52B13 [DX0001]
52B13H [DX0001]
52B23 [DX0001]
52B23H [DX0001]
52B33 [DX0001]
52B33H [DX0001]
5516A [DX0001]
5516AH [DX0001]
5517A [DX0001]
5517AH [DX0001]
DE2817A [DX0001]
DE2817A@PLCC32 [DX2032]
DE2817AH [DX0001]
DE2817AH@PLCC32 [DX2032]
DQ2817A [DX0001]
DQ2817A@PLCC32 [DX2032]
DQ2817AH [DX0001]
DQ2817AH@PLCC32 [DX2032]
DQ2864 [DX0001]
DQ2864@PLCC32 [DX2032]
DQ2864H [DX0001]
DQ2864H@PLCC32 [DX2032]
DQ28C256 [DX0001]
DQ28C256@PLCC32 [DX2032]
DQ28C64 [DX0001]

DQ28C64@PLCC32 [DX2032]
DQ28C64A@PLCC32 [DX2032]
DQ28C65@PLCC32 [DX2032]
DQ52B13H [DX0001]
E28C64@PLCC32 [DX2032]
E52B13H [DX0001]
E52B23H [DX0001]
E52B33H [DX0001]
M28C64@PLCC32 [DX2032]
M52B13H [DX0001]
M52B23H [DX0001]
M52B33H [DX0001]
PQ2864@PLCC32 [DX2032]
PQ2864H@PLCC32 [DX2032]
PQ28C64@PLCC32 [DX2032]
PQ28C65@PLCC32 [DX2032]
DQ28C64A [DX0001]
DQ28C65 [DX0001]
DQ52B13 [DX0001]
E28C64 [DX0001]
E52B13 [DX0001]
E52B23 [DX0001]
E52B33 [DX0001]
M28C64 [DX0001]
M52B13 [DX0001]
M52B23 [DX0001]
M52B33 [DX0001]
PQ2864 [DX0001]
PQ2864H [DX0001]
PQ28C64 [DX0001]
PQ28C65 [DX0001]

PLD

PALCE26V12H/4 [DX0001]
PALCE26V12H/4@SOIC28 [DX1033]
PALCE26V12H-15@PLCC28 [DX2028]
PALCE26V12H-20 [DX0001]
PALCE26V12H-20@SOIC28 [DX1033]
PALCE26V12H-25@PLCC28 [DX2028]
PALCE26V12H/4@PLCC28 [DX2028]
PALCE26V12H-15 [DX0001]
PALCE26V12H-15@SOIC28 [DX1033]
PALCE26V12H-20@PLCC28 [DX2028]
PALCE26V12H-25 [DX0001]
PALCE26V12H-25@SOIC28 [DX1033]

SEIKO

E(E)PROM/FRAM/NVRAM

S-22H10 [DX0001]
S-22H12 [DX0001]
S-22S10 [DX0001]
S-22S12 [DX0001]
S-24C01A(DP) [DX0001]
S-24C01A(FJA)@SOIC8 [DX1045]
S-24C01B(FJ)@SOIC8 [DX1045]
S-24C01CFM [DX0001]
S-24C01CPH [DX0001]
S-24C02A(DPA) [DX0001]
S-24C02B(DP) [DX0001]
S-24C02CFJ [DX1045]
S-24C02CFT [DX1059]
S-24C04A(DP) [DX0001]
S-24C04A(FJA)@SOIC8 [DX1045]
S-24C04B(FJ)@SOIC8 [DX1045]
S-22H10@SOP18 [DX1033]
S-22H12@SOP18 [DX1033]
S-22S10@SOP18 [DX1033]
S-22S12@SOP18 [DX1033]
S-24C01A(DPA) [DX0001]
S-24C01B(DP) [DX0001]
S-24C01CFJ [DX1045]
S-24C01CFT [DX1059]
S-24C02A(DP) [DX0001]
S-24C02A(FJA)@SOIC8 [DX1045]
S-24C02B(FJ)@SOIC8 [DX1045]
S-24C02CFM [DX0001]
S-24C02CPH [DX0001]
S-24C04A(DPA) [DX0001]
S-24C04B(DP) [DX0001]
S-24C04CFJ [DX1045]

S-24C04CFM [DX0001]
S-24C04CPH [DX0001]
S-24C08A(FJA)@SOIC8 [DX1045]
S-24C08CFM [DX0001]
S-24C08CPH [DX0001]
S-24C128CFM [DX0001]
S-24C128CPH [DX0001]
S-24C16A(FJA)@SOIC8 [DX1045]
S-24C16CFM [DX0001]
S-24C16CPH [DX0001]
S-24C256CFM [DX0001]
S-24C256CPH [DX0001]
S-24C32CFM [DX0001]
S-24C32CPH [DX0001]
S-24C512C-T8 [DX1059]
S-24C64CFM [DX0001]
S-24C64CPH [DX0001]
S-24CS01A(DP) [DX0001]
S-24CS01A(FT)@TSSOP8 [DX1059]
S-24CS02A(FJ)@SOIC8 [DX1045]
S-24CS04A(DP) [DX0001]
S-24CS04A(FT)@TSSOP8 [DX1059]
S-24CS08A(FJ)@SOIC8 [DX1045]
S-24CS16A(DP) [DX0001]
S-24CS16A(FT)@TSSOP8 [DX1059]
S-24CS64A(FT)@TSSOP8 [DX1059]
S-24H30@SOP8 [DX1079]
S-24H45@SOP8 [DX1079]
S-24S30@SOP8 [DX1079]
S-24S45@SOP8 [DX1079]
S-25A020A@SOP8 [DX1045]
S-25A080A@SOP8 [DX1045]
S-25A320A@SOP8 [DX1045]
S-25C010A@SOP8 [DX1045]
S-25C020A@SOP8 [DX1045]
S-25C040A@SOP8 [DX1045]
S-25C080A@SOP8 [DX1045]
S-25C128A@SOP8 [DX1045#1]
S-25C160A@SOP8 [DX1045]
S-25C256A@SOP8 [DX1045#1]
S-25C320A@SOP8 [DX1045]
S-25C512A@SOP8 [DX1045]
S-25C640A@SOP8 [DX1045]
S-25CM01A@SOP8 [DX1045]
S-2817A@SOP28(*) [DX1033]
S-2900A(FE)@SOP8 [DX1045]
S-2911(DP) [DX0001]
S-29130A(DPA) [DX0001]
S-24C04CFT [DX1059]
S-24C08A(DPA) [DX0001]
S-24C08CFJ [DX1045]
S-24C08CFT [DX1059]
S-24C128CFJ [DX1045]
S-24C128CFT [DX1045]
S-24C16A(DPA) [DX0001]
S-24C16CFJ [DX1045]
S-24C16CFT [DX1059]
S-24C256CFJ [DX1045]
S-24C256CFT [DX1045]
S-24C32CFJ [DX1045]
S-24C32CFT [DX1045]
S-24C512C-S8 [DX1044]
S-24C64CFJ [DX1045]
S-24C64CFT [DX1045]
S-24CM01C-S8 [DX1045]
S-24CS01A(FJ)@SOIC8 [DX1045]
S-24CS02A(DP) [DX0001]
S-24CS02A(FT)@TSSOP8 [DX1059]
S-24CS04A(FJ)@SOIC8 [DX1045]
S-24CS08A(DP) [DX0001]
S-24CS08A(FT)@TSSOP8 [DX1059]
S-24CS16A(FJ)@SOIC8 [DX1045]
S-24CS64A(FJ)@SOIC8 [DX1045]
S-24H30 [DX0001]
S-24H45 [DX0001]
S-24S30 [DX0001]
S-24S45 [DX0001]
S-25A010A@SOP8 [DX1045]
S-25A040A@SOP8 [DX1045]
S-25A160A@SOP8 [DX1045]
S-25A640A@SOP8 [DX1045]
S-25C010A@TSSOP8 [DX1059]
S-25C020A@TSSOP8 [DX1059]
S-25C040A@TSSOP8 [DX1059]
S-25C080A@TSSOP8 [DX1059]
S-25C128A@TSSOP8 [DX1059#1]
S-25C160A@TSSOP8 [DX1059]
S-25C256A@TSSOP8 [DX1059#1]
S-25C320A@TSSOP8 [DX1059]
S-25C512A@TSSOP8 [DX1059]
S-25C640A@TSSOP8 [DX1059]
S-2817A@SOP28 [DX1033]
S-2900A(DP) [DX0001]
S-2900A(UP)@SOT-89-5 [DX1041]
S-29130A(DFJA)@SOIC8 [DX1045]
S-29130A(FJA)@SOIC8 [DX1045]

S-29131A(DPA) [DX0001]
S-29190A(DPA) [DX0001]
S-29191A(DPA) [DX0001]
S-29194A(DPA) [DX0001]
S-29220A(DFJA)@SOIC8 [DX1045]
S-29220A(FJA)@SOIC8 [DX1045]
S-29221A(FJA)@SOIC8 [DX1045]
S-29230A(DPA) [DX0001]
S-29231A(DPA) [DX0001]
S-29290A(DPA) [DX0001]
S-29291A(DPA) [DX0001]
S-29294A(DPA) [DX0001]
S-29330A(DFJA)@SOIC8 [DX1045]
S-29330A(FJA)@SOIC8 [DX1045]
S-29331A(FJA)@SOIC8 [DX1045]
S-29390A(FJA)@SOIC8 [DX1045]
S-29391A(FJA)@SOIC8 [DX1045]
S-29394A(FJA)@SOIC8 [DX1045]
S-29430A@SOIC8 [DX1045]
S-29530A@SOIC8 [DX1045]
S-29630A@SOIC8 [DX1045]
S-29L130A(FE)@SOIC8 [DX1045]
S-29L131A(DFE)@SOIC8 [DX1045]
S-29L194A(DFE)@SOIC8 [DX1045]
S-29L220A(DFE)@SOIC8 [DX1045]
S-29L220A(FS)@SSOP8 [DX1059]
S-29L221A(FS)@SSOP8 [DX1059]
S-29L294A(FS)@TSSOP8 [DX1059]
S-29L330A(FE)@SOIC8 [DX1045]
S-29L331A(DFE)@SOIC8 [DX1045]
S-29L394A(DFE)@SOIC8 [DX1045]
S-29U130A(DFE)@SOIC8 [DX1045]
S-29U131A(DFE)@SOIC8 [DX1045]
S-29U194A(DFE)@SOIC8 [DX1045]
S-29U220A(DFE)@SOIC8 [DX1045]
S-29U221A(DFE)@SOIC8 [DX1045]
S-29U294A(DFE)@SOIC8 [DX1045]
S-29U330A(DFE)@SOIC8 [DX1045]
S-29U331A(DFE)@SOIC8 [DX1045]
S-29U394A(DFE)@SOIC8 [DX1045]
S-29Z330A(DFJA)@SOIC8 [DX1045]
S-29Z430A(DFJA)@SOIC8 [DX1045]
S-93A46A(D0A)@SOIC8 [DX1045]
S-93A66A(D0A)@SOIC8 [DX1045]
S-93A86A@SOIC8 [DX1045]
S-93C46A(DP) [DX0001]
S-93C46A(FT)@TSSOP8 [DX1059]
S-93C46B(FJ)@SOIC8 [DX1045]
S-29131A(FJA)@SOIC8 [DX1045]
S-29190A(FJA)@SOIC8 [DX1045]
S-29191A(FJA)@SOIC8 [DX1045]
S-29194A(FJA)@SOIC8 [DX1045]
S-29220A(DPA) [DX0001]
S-29221A(DPA) [DX0001]
S-29230A(DFJA)@SOIC8 [DX1045]
S-29230A(FJA)@SOIC8 [DX1045]
S-29231A(FJA)@SOIC8 [DX1045]
S-29290A(FJA)@SOIC8 [DX1045]
S-29291A(FJA)@SOIC8 [DX1045]
S-29294A(FJA)@SOIC8 [DX1045]
S-29330A(DPA) [DX0001]
S-29331A(DPA) [DX0001]
S-29390A(DPA) [DX0001]
S-29391A(DPA) [DX0001]
S-29394A(DPA) [DX0001]
S-29430A [DX0001]
S-29530A [DX0001]
S-29630A [DX0001]
S-29L130A(DFE)@SOIC8 [DX1045]
S-29L130A(FS)@SSOP8 [DX1059]
S-29L131A(FS)@SSOP8 [DX1059]
S-29L194A(FS)@TSSOP8 [DX1059]
S-29L220A(FE)@SOIC8 [DX1045]
S-29L221A(DFE)@SOIC8 [DX1045]
S-29L294A(DFE)@SOIC8 [DX1045]
S-29L330A(DFE)@SOIC8 [DX1045]
S-29L330A(FS)@SSOP8 [DX1059]
S-29L331A(FS)@SSOP8 [DX1059]
S-29L394A(FS)@TSSOP8 [DX1059]
S-29U130A(FS)@SSOP8 [DX1059]
S-29U131A(FS)@SSOP8 [DX1059]
S-29U194A(FS)@TSSOP8 [DX1059]
S-29U220A(FS)@SSOP8 [DX1059]
S-29U221A(FS)@SSOP8 [DX1059]
S-29U294A(FS)@TSSOP8 [DX1059]
S-29U330A(FS)@SSOP8 [DX1059]
S-29U331A(FS)@SSOP8 [DX1059]
S-29U394A(FS)@TSSOP8 [DX1059]
S-29Z330A(FS)@SSOP8 [DX1059]
S-29Z430A(FS)@SSOP8 [DX1059]
S-93A56A(D0A)@SOIC8 [DX1045]
S-93A66A(FJ)@SOIC8 [DX1045]
S-93C46A(DFJ)@SOIC8 [DX1045]
S-93C46A(FJ)@SOIC8 [DX1045]
S-93C46B(DP) [DX0001]
S-93C46B(FT)@TSSOP8 [DX1059]

S-93C56A(DFJ)@SOIC8 [DX1045]
S-93C56A(DP) [DX0001]
S-93C56A(FJ)@SOIC8 [DX1045]
S-93C56A(FT)@TSSOP8 [DX1059]
S-93C56B(DP) [DX0001]
S-93C56B(FJ)@SOIC8 [DX1045]
S-93C56B(FT)@TSSOP8 [DX1059]
S-93C66A(DFJ)@SOIC8 [DX1045]
S-93C66A(DP) [DX0001]
S-93C66A(FJ)@SOIC8 [DX1045]
S-93C66A(FT)@TSSOP8 [DX1059]
S-93C66B(DP) [DX0001]
S-93C66B(FJ)@SOIC8 [DX1045]
S-93C66B(FT)@TSSOP8 [DX1059]
S-93C76A(DP) [DX0001]
S-93C76A(FJ)@SOIC8 [DX1045]
S-93C76A(FT)@TSSOP8 [DX1059]
S-93C86A(DP) [DX0001]
S-93C86A(FJ)@SOIC8 [DX1045]
S-93C86A(FT)@TSSOP8 [DX1059]
S-93C86B@SOIC8 [DX1045]
S-93C86B@TSSOP8 [DX1059]
S-93L46A(DOI)@SOIC8 [DX1045]
S-93L46A(DOI)@TMSOP8 [DX1015]
S-93L46A(DOI)@TSSOP8 [DX1059]
S-93L46A(ROI)@SOIC8 [DX1045]
S-93L56A(DOI)@SOIC8 [DX1045]
S-93L56A(DOI)@TMSOP8 [DX1015]
S-93L56A(DOI)@TSSOP8 [DX1059]
S-93L56A(ROI)@SOIC8 [DX1045]
S-93L66A(DOI)@SOIC8 [DX1045]
S-93L66A(DOI)@TMSOP8 [DX1015]
S-93L66A(DOI)@TSSOP8 [DX1059]
S-93L66A(ROI)@SOIC8 [DX1045]
S-93L76A(DOI)@SOIC8 [DX1045]
S-93L76A(DOI)@TMSOP8 [DX1015]
S-93L76A(DOI)@TSSOP8 [DX1059]

SGS-THOMSON

E(E)PROM/FRAM/NVRAM

ET2716 [DX0001]
ETC2716 [DX0001]
ETC2732 [DX0001]
M24128 [DX0001]
M24128@SOIC8 [DX1045]
M24164 [DX0001]
M24164@SOIC8 [DX1045]
M24256 [DX0001]
M24256[3.9]@SOIC8 [DX1045]
M24256[5.5]@SOIC8 [DX1031]
M24512 [DX0001]
M24512@SOIC8 [DX1044]
M24512@TSOP8 [DX1059]
M24C04 [DX0001]
M24C04@SOIC8 [DX1045]
M24C08 [DX0001]
M24C08@SOIC8 [DX1045]
M24C08W [DX0001]
M24C08W@SOIC8 [DX1045]
M24C08W@TSOP8 [DX1059]
M24C64(BN) [DX0001]
M24C64(DL)@TSSOP14 [DX1000]
M24C64(DW)@TSSOP8 [DX1045]
M24C64(MN)@SOIC8 [DX1031]
M24C64(MW)@SOIC8 [DX1045]
M27128A [DX0001]
M2716 [DX0001]
M27256 [DX0001]
M27256A [DX0001]
M2732A [DX0001]
M27512 [DX0001]
M2764 [DX0001]
M2764A [DX0001]
M27C1000 [DX0001]
M27C1000@PLCC32 [DX2032]
M27C1000@TSOP32 [DX1002]
M27C1001 [DX0001]
M27C1001@PLCC32 [DX2032]
M27C1001@TSOP32 [DX1002]
M27C1024 [DX0001]
M27C1024@PLCC44 [DX2044]
M27C160 [DX0001]
M27C160@PLCC44 [DX2044]
M27C160@PSOP44 [DX1014]
M27C2001 [DX0001]
M27C2001@PLCC32 [DX2032]

M27C2001@TSOP32 [DX1002]
M27C202 [DX0001]
M27C202@PLCC44 [DX2044]
M27C202@VSOP40 [DX1005]
M27C256B [DX0001]
M27C256B@PLCC32 [DX2032]
M27C400 [DX0001]
M27C4001 [DX0001]
M27C4001@PLCC32 [DX2032]
M27C4001@TSOP32 [DX1002]
M27C4002 [DX0001]
M27C4002@PLCC44 [DX0001]
M27C405 [DX0001]
M27C405@PLCC32 [DX2032]
M27C405@TSOP32 [DX1002]
M27C512 [DX0001]
M27C512@PLCC32 [DX2032]
M27C516 [DX0001]
M27C516@PLCC44 [DX2044]
M27C64A [DX0001]
M27C64A@PLCC32 [DX2032]
M27C800 [DX0001]
M27C800@PLCC44 [DX2044]
M27C800@PSOP44 [DX1014]
M27C801 [DX0001]
M27C801@PLCC32 [DX2032]
M27C801@TSOP32 [DX1002]
M27HC641 [DX0001]
M27HC641@PLCC28 [DX2028]
M27HC642 [DX0001]
M27HC642@PLCC28 [DX2028]
M27V101 [DX0001]
M27V101@PLCC32 [DX2032]
M27V101@TSOP32 [DX1002]
M27V201 [DX0001]
M27V201@PLCC32 [DX2032]
M27V201@TSOP32 [DX1002]
M27V401 [DX0001]
M27V401@PLCC32 [DX2032]
M27V401@TSOP32 [DX1002]
M27V402 [DX0001]
M27V402@PLCC44 [DX2044]
M27V402@TSOP40 [DX1006]
M27V512 [DX0001]
M27V512@PLCC32 [DX2032]
M27V512@TSOP28 [DX1024]
M27V800 [DX0001]
M27V800@PLCC44 [DX2044]
M27V801 [DX0001]
M27V801@PLCC32 [DX2032]
M27V801@TSOP32 [DX1002]
M27W201 [DX0001]
M27W201@PLCC32 [DX2032]
M27W201@TSOP32 [DX1002]
M28010 [DX0001]
M28010@PLCC32 [DX2032]
M28010@TSOP32 [DX1002]
M28C16@PLCC32 [DX2032]
M28C64C [DX0001]
M28C64C@PLCC32 [DX2032]
M28C64C@SOIC28 [DX1033]
M28C64C@TSOP28 [DX1024]
M28F101 [DX0001]
M28F101(REVERSE)@TSOP32 [DX1002]
M28F101@PLCC32 [DX2032]
M28F101@TSOP32 [DX1002]
M28F102 [DX0001]
M28F102@PLCC44 [DX2044]
M28F102@TSOP40 [DX1005]
M28F151 [DX0001]
M28F151(REVERSE)@TSOP32 [DX1002]
M28F151@PLCC32 [DX2032]
M28F151@TSOP32 [DX1002]
M28F201 [DX0001]
M28F201(REVERSE)@TSOP32 [DX1002]
M28F201@PLCC32 [DX2032]
M28F201@TSOP32 [DX1002]
M28F210@PSOP44 [DX1014]
M28F210@TSOP48 [DX1004]
M28F211@TSOP40 [DX1006]
M28F220@PSOP44 [DX1014]
M28F220@TSOP48 [DX1004]
M28F221@TSOP40 [DX1006]
M28F256 [DX0001]
M28F256(REVERSE)@TSOP32 [DX1002]
M28F256@PLCC32 [DX2032]
M28F256@TSOP32 [DX1002]
M28F411@TSOP40 [DX1006]
M28F421@TSOP40 [DX1006]
M28F512 [DX0001]
M28F512(REVERSE)@TSOP32 [DX1002]
M28F512@PLCC32 [DX2032]
M28F512@TSOP32 [DX1002]
M29F002B [DX0001]
M29F002B@PLCC32 [DX2032]
M29F002B@TSOP32 [DX1002]

M29F002T [DX0001]
M29F002T@PLCC32 [DX2032]
M29F002T@TSOP32 [DX1002]
M29F040 [DX0001]
M29F040@PLCC32 [DX2032]
M29F040@TSOP32 [DX1002]
M29F040B [DX0001]
M29F040B@PLCC32 [DX2032]
M29F040B@TSOP32 [DX1002]
M29F100B@PSOP44 [DX1014]
M29F100B@TSOP48 [DX1004]
M29F100T@PSOP44 [DX1014]
M29F100T@TSOP48 [DX1004]
M29F102B@PLCC44 [DX2044]
M29F102B@TSOP40 [DX1005]
M29F102BB@PLCC44 [DX2044]
M29F102BB@TSOP40 [DX1005]
M29F200B@PSOP44 [DX1014]
M29F200B@TSOP48 [DX1004]
M29F200T@PSOP44 [DX1014]
M29F200T@TSOP48 [DX1004]
M29F400B@PSOP44 [DX1014]
M29F400B@TSOP48 [DX1004]
M29F400T@PSOP44 [DX1014]
M29F400T@TSOP48 [DX1004]
M29V040@PLCC32 [DX2032]
M29V040@TSOP32 [DX1002]
M29W008B@TSOP40 [DX1006]
M29W008T@TSOP40 [DX1006]
M29W040@PLCC32 [DX2032]
M29W040@TSOP32 [DX1002]
M29W400B@PSOP44 [DX1014]
M29W400B@TSOP48 [DX1004]
M29W400T@PLCC44 [DX1014]
M29W400T@TSOP48 [DX1004]
M29W512B@PLCC32 [DX2032]
M29W512B@TSOP32 [DX1003]
M29W800B@PSOP44 [DX1014]
M29W800B@TSOP48 [DX1004]
M29W800T@PSOP44 [DX1014]
M29W800T@TSOP48 [DX1004]
M48T35 [DX0001]
M48T35@SOIC28 [DX1033]
M48T35Y [DX0001]
M48T35Y@SOIC28 [DX1033]
M48T59 [DX0001]
M48T59@SOIC28 [DX1033]
M48T59Y [DX0001]
M48T59Y@SOIC28 [DX1033]
M48Z128 [DX0001]
M48Z128Y [DX0001]
M48Z30 [DX0001]
M48Z30Y [DX0001]
M48Z32 [DX0001]
M48Z32Y [DX0001]
M50FW080@PLCC32 [DX2032]
M50FW080@TSOP40 [DX1006]
M50FW080@VSOP32 [DX1003]
M87C257 [DX0001]
M87C257@PLCC32 [DX2032]
M93C06(08bit) [DX0001]
M93C06(08bit)@SOIC8 [DX1045]
M93C06(16bit) [DX0001]
M93C06(16bit)@SOIC8 [DX1045]
M93S46 [DX0001]
M93S46@SOIC8 [DX1045]
M93S46@TSSOP8
M95P02 [DX0001]
M95P02@SOIC8 [DX1045]
M95P04 [DX0001]
M95P04@SOIC8 [DX1045]
M95P08 [DX0001]
M95P08@SOIC8 [DX1045]
MK48C02 [DX0001]
MK48C02B [DX0001]
MK48C12 [DX0001]
MK48C12B [DX0001]
MK48T02 [DX0001]
MK48T02B [DX0001]
MK48T08 [DX0001]
MK48T12 [DX0001]
MK48T12B [DX0001]
MK48T18 [DX0001]
MK48Z02 [DX0001]
MK48Z02B [DX0001]
MK48Z08 [DX0001]
MK48Z12 [DX0001]
MK48Z12B [DX0001]
MK48Z18 [DX0001]
MKI48Z02 [DX0001]
MKI48Z02B [DX0001]
MKI48Z12 [DX0001]
MKI48Z12B [DX0001]
MKI48Z18 [DX0001]
ST24C01 [DX0001]
ST24C01@SOIC8 [DX1045]

ST24C02A [DX0001]
ST24C02A@SOIC8 [DX1045]
ST24C16 [DX0001]
ST24C16@SOIC8 [DX1045]
ST24W01 [DX0001]
ST24W01@SOIC8 [DX1045]
ST24W02 [DX0001]
ST24W02@SOIC8 [DX1045]
ST24W04C [DX0001]
ST24W04C@SOIC8 [DX1045]
ST27128A [DX0001]
ST27256 [DX0001]
ST2764A [DX0001]
ST27C256 [DX0001]
ST93C06(08bit) [DX0001]
ST93C06(08bit)@SOIC8 [DX1045]
ST93C06(16bit) [DX0001]
ST93C06(16bit)@SOIC8 [DX1045]
ST93CS46 [DX0001]
ST93CS46@SOIC8 [DX1045]
TS27C256 [DX0001]
TS27C64 [DX0001]
TS27C64@PLCC32 [DX2032]
TS27C64A [DX0001]
TS27C64A@PLCC32 [DX2032]
TS28C16A [DX0001]
TS28C17A [DX0001]

PLD

GAL16V8 [DX0001]
GAL16V8A [DX0001]

SHARP

E(E)PROM/FRAM/NVRAM

LH28F002SCHN@PSOP44 [DX1014]
LH28F002SCHT@TSOP40 [DX1006]
LH28F002SCN@PSOP44 [DX1014]
LH28F002SCT@TSOP40 [DX1006]
LH28F004BVE(BT)@TSOP40 [DX1006]
LH28F004BVE(TT)@TSOP40 [DX1006]
LH28F004BVHS(BT)@VSOP40 [DX1005]
LH28F004BVHS(TT)@VSOP40 [DX1005]
LH28F004BVT(BT)@TSOP40 [DX1006]
LH28F004BVT(TT)@TSOP40 [DX1006]
LH28F004SCHN@PSOP44 [DX1014]
LH28F004SCHS@VSOP40 [DX1005]
LH28F004SCHT@TSOP40 [DX1006]
LH28F004SCN@PSOP44 [DX1014]
LH28F004SCS@VSOP40 [DX1005]
LH28F004SCT@TSOP40 [DX1006]
LH28F008BJT(BTLZ1)@TSOP40 [DX1006]
LH28F008BJT(TB)@TSOP40 [DX1006]
LH28F008BJT(TT)@TSOP40 [DX1006]
LH28F008BJT(TTLZ2)@TSOP40 [DX1006]
LH28F008BVT(BT)@TSOP40 [DX1006]
LH28F008BVT(TT)@TSOP40 [DX1006]
LH28F008SAN@PSOP44 [DX1014]
LH28F008SAR@RTSOP40 [DX1006]
LH28F008SAT@TSOP40 [DX1006]
LH28F008SCH(L85)@RTSOP40 [DX1006]
LH28F008SCH-L@TSOP40 [DX1006]
LH28F008SCHN@PSOP44 [DX1014]
LH28F008SCH-V@TSOP40 [DX1006]
LH28F008SCH-ZU-120@TSOP40 [DX1006]
LH28F008SCN@PSOP44 [DX1014]
LH28F008SCN-L@PSOP44 [DX1014]
LH28F008SCT@TSOP40 [DX1006]
LH28F008SCT-L@TSOP40 [DX1006]
LH28F008SCT-V@TSOP40 [DX1006]
LH28F008SCV@TSOP40 [DX1006]
LH28F016SA@TSOP56 [DX1055]
LH28F016SC@PSOP44 [DX1014]
LH28F016SCR(L95)@RTSOP40 [DX1006]

LH28F016SCT-L95@TSOP40 [DX1006]　　LH28F016SUT@TSOP56 [DX1011]
LH28F128BFHBD@CSP72 [DX5001]　　LH28F128BFHE@TSOP48 [DX1004]
LH28F128BFHT(PBTL70_75A)@TSOP56 [DX1011]
LH28F128BFHT(PTTL70_75A)@TSOP56 [DX1011]
LH28F128BFHT(PTTLITA)@TSOP56 [DX1011]
LH28F128BFHT(PWTL80)@TSOP56 [DX1011]
LH28F128BFND@PSOP44 [DX1014]　　LH28F128SPHTD@TSOP56 [DX1055]
LH28F160BGB(B)@CSP48 [DX50UN]　　LH28F160BGB(T)@CSP48 [DX50UN]
LH28F160BGE(B)@TSOP48 [DX1004]　　LH28F160BGE(T)@TSOP48 [DX1004]
LH28F160BHBB@FBGA48 [DX50UN]　　LH28F160BHBT@FBGA48 [DX50UN]
LH28F160BHEB@TSOP48 [DX1004]　　LH28F160BHET@TSOP48 [DX1004]
LH28F160BJBB@FBGA48 [DX50UN]　　LH28F160BJBT@FBGA48 [DX50UN]
LH28F160BJD [DX0001]　　LH28F160BJEB@TSOP48 [DX1004]
LH28F160BJET@TSOP48 [DX1004]　　LH28F160BJHBB@FBGA48 [DX50UN]
LH28F160BJHBT@FBGA48 [DX50UN]
LH28F160BJHE(BTLZD)@TSOP48 [DX1004]
LH28F160BJHE(TTLZD)@TSOP48 [DX1004]
LH28F160BJHEB@TSOP48 [DX1004]　　LH28F160BJHET@TSOP48 [DX1004]
LH28F160BJHGB@FBGA48 [DX50UN]　　LH28F160BJHGT@FBGA48 [DX50UN]
LH28F160BVE(BTL)@TSOP48 [DX1004]　　LH28F160BVE(TTL)@TSOP48 [DX1004]
LH28F160BVEB(B)@CSP48 [DX50UN]　　LH28F160BVEB(T)@CSP48 [DX50UN]
LH28F160BVHE(BTL)@TSOP48 [DX1004]
LH28F160BVHE(TTL)@TSOP48 [DX1004]
LH28F160S3HNS@SSOP56 [DX1029]　　LH28F160S3HT@TSOP56 [DX1055]
LH28F160S3NS@SSOP56 [DX1029]　　LH28F160S3T@TSOP56 [DX1055]
LH28F160S5HNS@SSOP56 [DX1029]　　LH28F160S5HT@TSOP56 [DX1055]
LH28F160S5NS@SSOP56 [DX1029]　　LH28F160S5T@TSOP56 [DX1055]
LH28F160SKT@TSOP56 [DX1055]　　LH28F256BFHT(SL)@TSOP56 [DX1011]
LH28F256BFHT(TL)@TSOP56 [DX1011]　　LH28F320BFB(PB)@FBGA48 [DX5005]
LH28F320BFB(PT)@FBGA48 [DX5005]　　LH28F320BFE(PB)@TSOP48 [DX1004]
LH28F320BFE(PT)@TSOP48 [DX1004]　　LH28F320BFHB(PB)@FBGA48 [DX5005]
LH28F320BFHB(PT)@FBGA48 [DX5005]　　LH28F320BFHE(PB)@TSOP48 [DX1004]
LH28F320BFHE(PBTLZ2)@TSOP48 [DX1004]
LH28F320BFHE(PBTLZA)@TSOP48 [DX1004]
LH28F320BFHE(PT)@TSOP48 [DX1004]
LH28F320BFHE(PTTLE0)@TSOP48 [DX1004]
LH28F320BFHE(PTTLZ1)@TSOP48 [DX1004]
LH28F320BFHE(PTTLZ9)@TSOP48 [DX1004]
LH28F320BFHG(PBTLZL)@FBGA48 [DX5080]
LH28F320BFHG(PBTLZN)@FBGA48 [DX5080]
LH28F320BFHG(PTTLZ3)@FBGA48 [DX5080]
LH28F320BFHG(PTTLZK)@FBGA48 [DX5080]
LH28F320BFHG(PTTLZM)@FBGA48 [DX5080]
LH28F320BFN@PSOP44 [DX1014]　　LH28F320BJD [DX0001]
LH28F320BJE(PB)(OTP)@TSOP48 [DX1004]
LH28F320BJE(PB)@TSOP48 [DX1004]
LH28F320BJE(PT)(OTP)@TSOP48 [DX1004]
LH28F320BJE(PT)@TSOP48 [DX1004]

LH28F320BJHE(PB)(OTP)@TSOP48 [DX1004]
LH28F320BJHE(PT)(OTP)@TSOP48 [DX1004]
LH28F320BJN@PSOP44 [DX1014]
LH28F320BMN@PSOP44 [DX1014]
LH28F320S3HNS@SSOP56 [DX1029]
LH28F320S3HT@TSOP56 [DX1055]
LH28F320S3NS@SSOP56 [DX1029]
LH28F320S3T@TSOP56 [DX1055]
LH28F320S3TD@TSOP56 [DX1055]
LH28F320S5HNS@SSOP56 [DX1029]
LH28F320S5HT@TSOP56 [DX1055]
LH28F320S5NS@SSOP56 [DX1029]
LH28F320S5T@TSOP56 [DX1055]
LH28F320SKTD@TSOP56 [DX1055]
LH28F320SUTD@TSOP56 [DX1055]
LH28F400BGB(B)@CSP48 [DX50UN]
LH28F400BGB(T)@CSP48 [DX50UN]
LH28F400BGE(B)@TSOP48 [DX1004]
LH28F400BGE(T)@TSOP48 [DX1004]
LH28F400BGHB(B)@CSP48 [DX50UN]
LH28F400BGHB(T)@CSP48 [DX50UN]
LH28F400BGHE(B)@TSOP48 [DX1004]
LH28F400BGHE(T)@TSOP48 [DX1004]
LH28F400BGN(B)@PSOP44 [DX1014]
LH28F400BGN(T)@PSOP44 [DX1014]
LH28F400BVB(B)@CSP48 [DX50UN]
LH28F400BVB(T)@CSP48 [DX50UN]
LH28F400BVE(B)@TSOP48 [DX1004]
LH28F400BVE(T)@TSOP48 [DX1004]
LH28F400BVHB(B)@CSP48 [DX50UN]
LH28F400BVHB(T)@CSP48 [DX50UN]
LH28F400BVHE(B)@TSOP48 [DX1004]
LH28F400BVHE(T)@TSOP48 [DX1004]
LH28F400BVN(B)@PSOP44 [DX1014]
LH28F400BVN(T)@PSOP44 [DX1014]
LH28F512BFBD(PTSLZ2)@CSP72 [DX5001]
LH28F512BFBD(PTSLZ4)@CSP72 [DX5001]
LH28F640BFB(PB)@FBGA60 [DX5007]
LH28F640BFB(PT)@FBGA60 [DX5007]
LH28F640BFE(PB)@TSOP48 [DX1004]
LH28F640BFE(PT)@TSOP48 [DX1004]
LH28F640BFHB(PB)@FBGA60 [DX5007]
LH28F640BFHB(PT)@FBGA60 [DX5007]
LH28F640BFHBD@SSOP56 [DX0051]
LH28F640BFHE(PB)@TSOP48 [DX1004]
LH28F640BFHE(PBTL70A@TSOP48 [DX1004]
LH28F640BFHE(PT)@TSOP48 [DX1004]
LH28F640BFHE(PTTL70A@TSOP48 [DX1004]
LH28F640BFHE(PTTLHIA@TSOP48 [DX1004]
LH28F640BFHG(PTTLZ6)@FBGA48 [DX5085]
LH28F640BNHG(PBSL60)@CSP56 [DX5093]
LH28F640BNHG(PTSL70)@CSP56 [DX5093]
LH28F640SPHT@TSOP56 [DX1055]
LH28F800BGB(B)@CSP48 [DX50UN]
LH28F800BGB(T)@CSP48 [DX50UN]
LH28F800BGE(B)@TSOP48 [DX1004]
LH28F800BGE(T)@TSOP48 [DX1004]
LH28F800BGHB(B)@CSP48 [DX50UN]
LH28F800BGHB(T)@CSP48 [DX50UN]
LH28F800BGHE(B)@TSOP48 [DX1004]
LH28F800BGHE(T)@TSOP48 [DX1004]
LH28F800BGHE(TTL10)@TSOP48 [DX1004]
LH28F800BGN(B)@PSOP44 [DX1014]
LH28F800BGN(T)@PSOP44 [DX1014]
LH28F800BH-B@TSOP48 [DX1004]
LH28F800BJE(PB)(OTP)@TSOP48 [DX1004]
LH28F800BJE(PB)@TSOP48 [DX1004]
LH28F800BJE(PT)(OTP)@TSOP48 [DX1004]
LH28F800BJE(PT)@TSOP48 [DX1004]
LH28F800BJHE(PB)(OTP)@TSOP48 [DX1004]
LH28F800BJHE(PT)(OTP)@TSOP48 [DX1004]
LH28F800BJHG(PB)(OTP)@CSP48 [DX50UN]
LH28F800BJR(PT)(OTP)@TSOP48 [DX1004]

LH28F800BVB(B)@CSP48 [DX50UN]
LH28F800BVB(T)@CSP48 [DX50UN]
LH28F800BV-B@TSOP48 [DX1004]
LH28F800BVE(B)@TSOP48 [DX1004]
LH28F800BVE(T)@TSOP48 [DX1004]
LH28F800BVE(TV85)@TSOP48 [DX1004]
LH28F800BVHB(B)@CSP48 [DX50UN]
LH28F800BVHB(T)@CSP48 [DX50UN]
LH28F800BVHB@TSOP48 [DX1004]
LH28F800BVHE(B)@TSOP48 [DX1004]
LH28F800BVHE(T)@TSOP48 [DX1004]
LH28F800BVHT@TSOP48 [DX1004]
LH28F800BVN(B)@PSOP44 [DX1014]
LH28F800BVN(T)@PSOP44 [DX1014]
LH28F800BVN(TV85)@PSOP44 [DX1014]
LH28F800BV-T@TSOP48 [DX1004]
LH28F800SG(L100)@TSOP48 [DX1004]
LH28F800SG(L120)@TSOP48 [DX1004]
LH28F800SG(L70)@TSOP48 [DX1004]
LH28F800SG(L80)@TSOP48 [DX1004]
LH28F800SG(L85)@TSOP48 [DX1004]
LH28F800SGH(L100)@TSOP48 [DX1004]
LH28F800SGH(L120)@TSOP48 [DX1004]
LH28F800SGH(L70)@TSOP48 [DX1004]
LH28F800SGH(L80)@TSOP48 [DX1004]
LH28F800SGH(L85)@TSOP48 [DX1004]
LH28F800SGHE(L70)@TSOP48 [DX1004]
LH28F800SUT@TSOP56 [DX1011]
LHF00L03@PLCC32 [DX2032]
LHF00L04@TSOP40 [DX1006]
LHF00L06@TSOP40 [DX1006]
LHF00L07@PLCC32 [DX2032]
LHF00L08(LH28F320T)@FBGA48 [DX5002]
LHF00L09(LH28F320B)@FBGA48 [DX5002]
LHF00L10(LH28F320T)@FBGA48 [DX5080]
LHF00L11(LH28F320B)@FBGA48 [DX5080]
LHF00L12(LH28F320T)@TSOP48 [DX1004]
LHF00L13(LH28F320B)@TSOP48 [DX1004]
LHF00L14(LH28F320T)@TSOP48 [DX1004]
LHF00L15(LH28F320B)@TSOP48 [DX1004]
LHF00L24(LH28F160T)@FBGA48 [DX5002]
LHF00L25(LH28F160B)@FBGA48 [DX5002]
LHF00L28(LH28F160T)@TSOP48 [DX1004]
LHF00L29(LH28F160B)@TSOP48 [DX1004]
LHF00L30(LH28F160T)@TSOP48 [DX1004]
LHF00L31(LH28F160B)@TSOP48 [DX1004]
LRS1311@FBGA72 [DX5001]
LRS1311A@FBGA72 [DX5001]
LRS1315@FBGA72 [DX5001]
LRS1315D@FBGA72 [DX5001]
LRS1316@FBGA72 [DX5001]
LRS1316A@FBGA72 [DX5001]
LRS1317@FBGA72 [DX5001]
LRS1320@FBGA72 [DX5001]
LRS1320A@FBGA72 [DX5001]
LRS1329@FBGA72 [DX5001]
LRS1329A@FBGA72 [DX5001]
LRS1330@FBGA72 [DX5001]
LRS1330A@FBGA72 [DX5001]
LRS1330B@FBGA72 [DX5001]
LRS1330D@FBGA72 [DX5001]
LRS1331@FBGA72 [DX5001]
LRS1331B@FBGA72 [DX5001]
LRS1331C@FBGA72 [DX5001]
LRS1336@FBGA72 [DX5001]
LRS1339@FBGA72 [DX5001]
LRS1341@FBGA72 [DX5001]
LRS1341A@FBGA72 [DX5001]
LRS1342@FBGA72 [DX5001]
LRS1342A@FBGA72 [DX5001]
LRS1348@FBGA72 [DX5001]
LRS1348B@FBGA72 [DX5001]
LRS1348E@FBGA72 [DX5001]
LRS1350@FBGA72 [DX5001]

LRS1356@FBGA72 [DX5001]
LRS1360@FBGA72 [DX5001]
LRS1360C@FBGA72 [DX5001]
LRS1370@FBGA72 [DX5001]
LRS1370B@FBGA72 [DX5001]
LRS1380@FBGA72 [DX5001]
LRS1381@FBGA72 [DX5001]
LRS1382@FBGA72 [DX5001]
LRS1383@FBGA72 [DX5001]
LRS1383C@FBGA72 [DX5001]
LRS1383F@FBGA72 [DX5001]
LRS1384@FBGA72 [DX5001]
LRS1385@FBGA72 [DX5001]
LRS1386@FBGA72 [DX5001]
LRS1387@FBGA72 [DX5001]
LRS1391@FBGA72 [DX5001]
LRS1392A@FBGA72 [DX5001]
LRS1393A@FBGA72 [DX5001]
LRS1393C@FBGA72 [DX5001]
LRS1395@FBGA72 [DX5001]
LRS1396@TSOP56 [DX1055]
LRS13A0@FBGA72 [DX5001]
LRS13A1@FBGA72 [DX5001]
LRS13A2@FBGA72 [DX5001]
LRS13A3@FBGA72 [DX5001]
LRS13A4@FBGA72 [DX5001]
LRS13A5@FBGA72 [DX5001]
LRS13A6@FBGA72 [DX5001]
LRS13A8@TSOP56 [DX1055]
LRS1805A@FBGA72 [DX5001]
LRS1806A@FBGA72 [DX5001]
LRS1806C@FBGA72 [DX5001]
LRS1806F@FBGA72 [DX5001]
LRS1806J@FBGA72 [DX5001]
LRS1807A@FBGA72 [DX5001]
LRS1808@FBGA72 [DX5001]
LRS1808A@FBGA72 [DX5001]
LRS1811@FBGA72 [DX5001]
LRS1811A@FBGA72 [DX5001]
LRS1812@FBGA72 [DX5001]
LRS1815@FBGA72 [DX5001]
LRS1816@FBGA72 [DX5001]
LRS1816A@FBGA72 [DX5001]
LRS1821@FBGA72 [DX5001]
LRS1822@FBGA72 [DX5001]
LRS1825@FBGA72 [DX5001]
LRS1826@FBGA72 [DX5001]
LRS1826A@FBGA72 [DX5001]
LRS1827@FBGA72 [DX5001]
LRS1828@FBGA72 [DX5001]
LRS1828B@FBGA72 [DX5001]
LRS1828C@FBGA72 [DX5001]
LRS1829@FBGA72 [DX5001]
LRS1832@FBGA72 [DX5001]
LRS1834@FBGA72 [DX5001]
LRS1844@FBGA72 [DX5001]
LRS1845@FBGA72 [DX5001]
LRS1850@FBGA72 [DX5001]
LRS1851@FBGA72 [DX5001]
LRS1852@FBGA72 [DX5001]
LRS1853@FBGA72 [DX5001]
LRS1857@FBGA72 [DX5001]
LRS18621@FBGA72 [DX5001]
LRS1862E@FBGA72 [DX5001]
LRS1864@FBGA72 [DX5001]
LRS18641@FBGA72 [DX5001]
LRS1864A@FBGA72 [DX5001]
LRS1871@FBGA72 [DX5001]
LRS18712@FBGA72 [DX5001]
LRS1871A@FBGA72 [DX5001]
LRS1872@FBGA72 [DX5001]
LRS18722@FBGA72 [DX5001]
LRS1872A@FBGA72 [DX5001]
LRS1874@FBGA72 [DX5001]
LRS1875@FBGA72 [DX5001]
LRS18751@FBGA72 [DX5001]
LRS1876@FBGA72 [DX5001]
LRS18761@FBGA72 [DX5001]
LRS1876A@FBGA72 [DX5001]
LRS18791@FBGA72 [DX5001]
LRS18811@FBGA72 [DX5001]
LRS18821@FBGA72 [DX5001]
LRS18831@FBGA72 [DX5001]
LRS18841@FBGA72 [DX5001]
LRS1890@FBGA72 [DX5001]
LRS1891@FBGA72 [DX5001]
LRS1892@FBGA72 [DX5001]
LRS18941@FBGA72 [DX5001]
LRS1896@FBGA72 [DX5001]
LRS1897@FBGA72 [DX5001]
LRS1898@FBGA72 [DX5001]
LRS18A1@FBGA72 [DX50UN]
LRS18A2@FBGA72 [DX50UN]
LRS18A3@FBGA72 [DX50UN]
LRS18A4@FBGA72 [DX50UN]
LRS18A7@FBGA88 [DX50UN]

LRS18A8@FBGA88 [DX50UN]
LRS18A9@FBGA88 [DX50UN]
LRS18AA@FBGA88 [DX50UN]
LRS18AB@FBGA88 [DX50UN]
LRS18AC@FBGA88 [DX50UN]
LRS18AD@FBGA88 [DX50UN]
LRS18AE@FBGA88 [DX50UN]
LRS18AF@FBGA88 [DX50UN]
LRS18AG@FBGA88 [DX50UN]
LRS18AH@FBGA88 [DX50UN]
LRS18AJ@FBGA88 [DX50UN]
LRS18AK@FBGA72 [DX50UN]
LRS18AL@FBGA72 [DX50UN]
LRS18AM@FBGA88 [DX50UN]
LRS18AN@FBGA88 [DX50UN]
LRS18AS@FBGA88 [DX50UN]
LRS18AT@FBGA88 [DX50UN]
LRS18AU@FBGA88 [DX50UN]
LRS18AV@FBGA88 [DX50UN]
LRS18AW@FBGA88 [DX50UN]
LRS18AY@FBGA88 [DX50UN]
LRS18AZ@FBGA88 [DX50UN]
LRS18B0@FBGA72 [DX5001]
LRS18B1@FBGA88 [DX5001]
LRS18B2@FBGA88 [DX5001]
LRS18B4@FBGA88 [DX5001]
LRS18B5@FBGA88 [DX5001]
LRS18B6@FBGA88 [DX5001]
LRS18B7@FBGA88 [DX5001]
LRS18B8@FBGA88 [DX5001]
LRS18B9@FBGA88 [DX5001]
LRS18BE@FBGA88 [DX5001]
LRS18BF@FBGA88 [DX5001]
LRS18BG@FBGA88 [DX5001]
LRS18BH@FBGA88 [DX5001]
LRS18BK@FBGA88 [DX5001]
LRS18BL@FBGA88 [DX5001]
LRS18BM@FBGA88 [DX5001]
LRS18BN@FBGA88 [DX5001]
LRS18BS@FBGA72 [DX5001]
LRS18BT@FBGA72 [DX5001]
LRS18BU@FBGA88 [DX5001]
LRS18C8A@FBGA72 [DX5001]
LRS18C8G@FBGA72 [DX5001]
LRS1B02@FBGA72 [DX5001]
LRS1B04@FBGA72 [DX5001]
LRS1B05@FBGA72 [DX5001]
LRS1B06@FBGA72 [DX5001]
LRS1B07@FBGA72 [DX5001]
LRS1B12@FBGA72 [DX5001]
LRS1B30@FBGA72 [DX5001]

SHENHUI

E(E)PROM/FRAM/NVRAM

RD48F4400L0ZDQ2P [DX0001]
RD48F4400L0ZDQ5P [DX0001]

SIEMENS

E(E)PROM/FRAM/NVRAM

SDA2526 [DX0001]
SDA2526@SOIC8 [DX1045]
SDA2546 [DX0001]
SDA2546@SOIC8 [DX1045]
SDA25X26 [DX0001]
SDA25X26@SOIC8 [DX1045]
SDA25X46 [DX0001]
SDA25X46@SOIC8 [DX1045]
SDE2526 [DX0001]
SDE2526@SOIC8 [DX1045]
SDE2546 [DX0001]
SDE2546@SOIC8 [DX1045]
SDE25X26 [DX0001]
SDE25X26@SOIC8 [DX1045]
SDE25X46 [DX0001]
SDE25X46@SOIC8 [DX1045]
SLA24C01 [DX0001]
SLA24C01@SOIC8 [DX1045]

SLA24C02 [DX0001]
SLA24C04 [DX0001]
SLA24C08 [DX0001]
SLA24C16 [DX0001]
SLA24C164 [DX0001]
SLA24C32 [DX0001]
SLA24C64 [DX0001]
SLA25010 [DX0001]
SLA25020 [DX0001]
SLA25040 [DX0001]
SLA25080 [DX0001]
SLA25160 [DX0001]
SLE24C01 [DX0001]
SLE24C02 [DX0001]
SLE24C04 [DX0001]
SLE24C08 [DX0001]
SLE24C16 [DX0001]
SLE24C164 [DX0001]
SLE24C32 [DX0001]
SLE24C64 [DX0001]
SLE25010 [DX0001]
SLE25020 [DX0001]
SLE25040 [DX0001]
SLE25080 [DX0001]
SLE25160 [DX0001]

SLA24C02@SOIC8 [DX1045]
SLA24C04@SOIC8 [DX1045]
SLA24C08@SOIC8 [DX1045]
SLA24C16@SOIC8 [DX1045]
SLA24C164@SOIC8 [DX1045]
SLA24C32@SOIC8 [DX1045]
SLA24C64@SOIC8 [DX1045]
SLA25010@SOIC8 [DX1045]
SLA25020@SOIC8 [DX1045]
SLA25040@SOIC8 [DX1045]
SLA25080@SOIC8 [DX1045]
SLA25160@SOIC8 [DX1045]
SLE24C01@SOIC8 [DX1045]
SLE24C02@SOIC8 [DX1045]
SLE24C04@SOIC8 [DX1045]
SLE24C08@SOIC8 [DX1045]
SLE24C16@SOIC8 [DX1045]
SLE24C164@SOIC8 [DX1045]
SLE24C32@SOIC8 [DX1045]
SLE24C64@SOIC8 [DX1045]
SLE25010@SOIC8 [DX1045]
SLE25020@SOIC8 [DX1045]
SLE25040@SOIC8 [DX1045]
SLE25080@SOIC8 [DX1045]
SLE25160@SOIC8 [DX1045]

MICROCONTROLLER

SAB-C501G-1E [DX0001]
SAB-C501G-1E@TQFP44 [DX3002]
SAB-C505A-4EM@TQFP44 [DX3002]
SAB-C505L-4EM@PQFP80 [DX3018]
SAB-C508-4EP@SDIP64 [DX0064]
SAB-C540U-1EN@PLCC44 [DX2044]
SAB-C541U-1EN@PLCC44 [DX2044]
SAB-XC161CS-32F20F@TQFP144 [DX3035]
SAB-XC161CS-32F40F@TQFP144 [DX3035]
SAB-XC167CI-16F20F@TQFP144 [DX3035]
SAB-XC167CI-16F40F@TQFP144 [DX3035]
SAB-XC167CI-32F20F@TQFP144 [DX3035]
SAB-XC167CI-32F40F@TQFP144 [DX3035]
SAF-C164CI-8EM@TQFP80 [DX3018]
SAF-C501G-1EP [DX0001]
SAF-C505A-4EM@TQFP44 [DX3002]
SAF-C505L-4EM@PQFP80 [DX3018]
SAF-C508-4EP@SDIP64 [DX0064]
SAF-C513AO-2EN@PLCC44 [DX2044]

SAB-C501G-1E@PLCC44 [DX2044]
SAB-C504-2EM@TQFP44 [DX3002]
SAB-C505CA-4EM@TQFP44 [DX3002]
SAB-C508-4EM@TQFP64 [DX3014]
SAB-C515C-8EM@TQFP80 [DX3018]
SAB-C540U-1EP@SDIP52 [DX0052]
SAB-C541U-1EP@SDIP52 [DX0052]

SAF-C501G-1EN@PLCC44 [DX2044]
SAF-C504-2EM@TQFP44 [DX3002]
SAF-C505CA-4EM@TQFP44 [DX3002]
SAF-C508-4EM@TQFP64 [DX3014]
SAF-C513AO-2EM@TQFP44 [DX3002]
SAF-C513AO-2EP [DX0001]

SAF-C515C-8EM@TQFP80 [DX3018]
SAF-XC161CJ-16F20F@TQFP144 [DX3035]
SAF-XC161CJ-16F40F@TQFP144 [DX3035]
SAF-XC161CS-32F20F@TQFP144 [DX3035]
SAF-XC161CS-32F40F@TQFP144 [DX3035]
SAF-XC164CM-16F20F@TQFP64 [DX3011]
SAF-XC164CM-16F40F@TQFP64 [DX3011]
SAF-XC164CM-4F20F@TQFP64 [DX3011]
SAF-XC164CM-4F40F@TQFP64 [DX3011]
SAF-XC164CM-8F20F@TQFP64 [DX3011]
SAF-XC164CM-8F40F@TQFP64 [DX3011]
SAF-XC164CS-16F20F@TQFP100 [DX3021]
SAF-XC164CS-16F40F@TQFP100 [DX3021]
SAF-XC164CS-32F20F@TQFP100 [DX3021]
SAF-XC164CS-32F40F@TQFP100 [DX3021]
SAF-XC164CS-8F20F@TQFP100 [DX3021]
SAF-XC164CS-8F40F@TQFP100 [DX3021]
SAF-XC164D-16F20F@TQFP100 [DX3021]
SAF-XC164D-16F40F@TQFP100 [DX3021]
SAF-XC164D-8F20F@TQFP100 [DX3021]
SAF-XC164D-8F40F@TQFP100 [DX3021]
SAF-XC164N-16F20F@TQFP100 [DX3021]
SAF-XC164N-16F40F@TQFP100 [DX3021]
SAF-XC164N-8F20F@TQFP100 [DX3021]
SAF-XC164N-8F40F@TQFP100 [DX3021]
SAF-XC164S-16F20F@TQFP100 [DX3021]
SAF-XC164S-16F40F@TQFP100 [DX3021]
SAF-XC164S-8F20F@TQFP100 [DX3021]
SAF-XC164S-8F40F@TQFP100 [DX3021]
SAF-XC167CI-16F20F@TQFP144 [DX3035]
SAF-XC167CI-16F40F@TQFP144 [DX3035]
SAF-XC167CI-32F20F@TQFP144 [DX3035]
SAF-XC167CI-32F40F@TQFP144 [DX3035]
SAF-XC2210U-4FXRTSSOP38 [DX1012] SAF-XC2210U-8FXRTSSOP38 [DX1012]
SAF-XC2220L-12FXV@QFN48 [DX4021] SAF-XC2220L-20FXV@QFN48 [DX4021]
SAF-XC2220U-4FXV@QFN48 [DX4021] SAF-XC2220U-8FXV@QFN48 [DX4021]
SAF-XC2224L-12FXV@QFN48 [DX4021] SAF-XC2224L-20FXV@QFN48 [DX4021]
SAF-XC2230L-12F66L@QFP64 [DX3011]
SAF-XC2230L-20F66L@QFP64 [DX3011]
SAF-XC2234L-12F66L@QFP64 [DX3011]
SAF-XC2234L-20F66L@QFP64 [DX3011]
SAF-XC2261N-16F40L@QFP100 [DX3043]
SAF-XC2261N-16F80L@QFP100 [DX3043]
SAF-XC2261N-24F40L@QFP100 [DX3043]
SAF-XC2261N-24F80L@QFP100 [DX3043]
SAF-XC2263M-104F80L@TQFP100 [DX3043]
SAF-XC2263M-56F80L@QFP100 [DX3043]
SAF-XC2263M-72F80L@QFP100 [DX3043]

SAF-XC2263N-16F40L@QFP100 [DX3043]
SAF-XC2263N-16F80L@QFP100 [DX3043]
SAF-XC2263N-24F40L@QFP100 [DX3043]
SAF-XC2263N-24F80L@QFP100 [DX3043]
SAF-XC2263N-40F40L@QFP100 [DX3043]
SAF-XC2263N-40F80L@QFP100 [DX3043]
SAF-XC2264M-104F80L@TQFP100 [DX3043]
SAF-XC2264M-56F80L@QFP100 [DX3043]
SAF-XC2264M-72F80L@QFP100 [DX3043]
SAF-XC2264N-16F40L@QFP100 [DX3043]
SAF-XC2264N-16F80L@QFP100 [DX3043]
SAF-XC2264N-24F40L@QFP100 [DX3043]
SAF-XC2264N-24F80L@QFP100 [DX3043]
SAF-XC2264N-40F40L@QFP100 [DX3043]
SAF-XC2264N-40F80L@QFP100 [DX3043]
SAF-XC2265M-104F80L@TQFP100 [DX3043]
SAF-XC2265M-56F80L@QFP100 [DX3043]
SAF-XC2265M-72F80L@QFP100 [DX3043]
SAF-XC2265N-16F40L@QFP100 [DX3043]
SAF-XC2265N-16F80L@QFP100 [DX3043]
SAF-XC2265N-24F40L@QFP100 [DX3043]
SAF-XC2265N-24F80L@QFP100 [DX3043]
SAF-XC2265N-40F40L@QFP100 [DX3043]
SAF-XC2265N-40F80L@QFP100 [DX3043]
SAF-XC2267M-104F80L@TQFP100 [DX3043]
SAF-XC2267M-56F80L@QFP100 [DX3043]
SAF-XC2267M-72F80L@QFP100 [DX3043]
SAF-XC2268M-104F80L@TQFP100 [DX3043]
SAF-XC2268M-56F80L@QFP100 [DX3043]
SAF-XC2268M-72F80L@QFP100 [DX3043]
SAF-XC2268N-16F40L@QFP100 [DX3043]
SAF-XC2268N-16F80L@QFP100 [DX3043]
SAF-XC2268N-24F40L@QFP100 [DX3043]
SAF-XC2268N-24F80L@QFP100 [DX3043]
SAF-XC2268N-40F40L@QFP100 [DX3043]
SAF-XC2268N-40F80L@QFP100 [DX3043]
SAF-XC2285-72F66L@TQFP144 [DX3035]
SAF-XC2285-96F66L@TQFP144 [DX3035]
SAF-XC2286-72F66L@TQFP144 [DX3035]
SAF-XC2286-96F66L@TQFP144 [DX3035]
SAF-XC2287-72F66L@TQFP144 [DX3035]
SAF-XC2287-96F66L@TQFP144 [DX3035]
SAF-XC2336B-24F66L@QFP64 [DX3011]
SAF-XC2336B-40F66L@QFP64 [DX3011]
SAF-XC2361B-24F80L@QFP100 [DX3043]
SAF-XC2361B-40F80L@QFP100 [DX3043]
SAF-XC2363B-24F80L@QFP100 [DX3043]
SAF-XC2363B-40F80L@QFP100 [DX3043]

SAF-XC2364B-24F80L@QFP100 [DX3043]
SAF-XC2364B-40F80L@QFP100 [DX3043]
SAF-XC2365B-24F80L@QFP100 [DX3043]
SAF-XC2365B-40F80L@QFP100 [DX3043]
SAF-XC2387-72F66L@TQFP144 [DX3035]
SAF-XC2734X-40F80L@QFP64 [DX3011]
SAF-XC2764X-40F80L@QFP100 [DX3043]
SAF-XC822-1FRI@TSSOP16 [DX1000]
SAF-XC822M-1FRI@TSSOP16 [DX1000]
SAF-XC822MT-1FRI@TSSOP16 [DX1000]
SAF-XC822T-0FRI@TSSOP16 [DX1000]
SAF-XC822T-1FRI@TSSOP16 [DX1000]
SAF-XC824M-1FGI@SOIC20 [DX1033]
SAF-XC824MT-1FGI@SOIC20 [DX1033]
SAF-XC835MT-2FGI@SOIC24 [DX1033]
SAF-XC836-2FRI@TSSOP28 [DX1001]
SAF-XC836M-1FRI@TSSOP28 [DX1001]
SAF-XC836M-2FRI@TSSOP28 [DX1001]
SAF-XC836MT-2FRA@TSSOP28 [DX1001]
SAF-XC836MT-2FRI@TSSOP28 [DX1001]
SAF-XC836T-2FRI@TSSOP28 [DX1001]
SAF-XC846-1FR@TSSOP38 [DX1012]
SAF-XC856CLM-13FFI@QFP64 [DX3011]
SAF-XC856CLM-16FFI@QFP64 [DX3011]
SAF-XC856CLM-9FFI@QFP64 [DX3011]
SAF-XC856LM-13FFI@QFP64 [DX3011]
SAF-XC856LM-16FFI@QFP64 [DX3011]
SAF-XC856LM-9FFI@QFP64 [DX3011]
SAF-XC858CA-13FFI(5v)QFP64 [DX3011]
SAF-XC858CA-16FFI(5v)QFP64 [DX3011]
SAF-XC858CA-9FFI(5v)QFP64 [DX3011]
SAF-XC866-1FR@TSSOP38 [DX1012]
SAF-XC866-2FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866-2FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866-4FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866-4FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866L-2FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866L-2FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC866L-4FR(A STEP)@TSSOP38 [DX1012]
SAF-XC866L-4FR(BB STEP)@TSSOP38 [DX1012]
SAF-XC878-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878-13FFI(5v)@QFP64 [DX3011]
SAF-XC878-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878-16FFI(5v)@QFP64 [DX3011]
SAF-XC878CM-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878CM-13FFI(5v)@QFP64 [DX3011]
SAF-XC878CM-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878CM-16FFI(5v)@QFP64 [DX3011]
SAF-XC878M-13FFI(3.3v)@QFP64 [DX3011]
SAF-XC878M-13FFI(5v)@QFP64 [DX3011]
SAF-XC878M-16FFI(3.3v)@QFP64 [DX3011]
SAF-XC878M-16FFI(5v)@QFP64 [DX3011]
SAF-XC886-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886-6FFA(5v)@QFP48 [DX3007]
SAF-XC886-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886-6FFI(5v)@QFP48 [DX3007]

SAF-XC886-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886-8FFA(5v)@QFP48 [DX3007]
SAF-XC886-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886-8FFI(5v)@QFP48 [DX3007]
SAF-XC886C-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886C-6FFA(5v)@QFP48 [DX3007]
SAF-XC886C-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886C-6FFI(5v)@QFP48 [DX3007]
SAF-XC886C-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886C-8FFA(5v)@QFP48 [DX3007]
SAF-XC886C-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886C-8FFI(5v)@QFP48 [DX3007]
SAF-XC886CLM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886CLM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886CLM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886CLM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CLM-8FFI(5v)@QFP48 [DX3007]
SAF-XC886CM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886CM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886CM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886CM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886CM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886CM-8FFI(5v)@QFP48 [DX3007]
SAF-XC886LM-6FFA(3.3v)@QFP48 [DX3007]
SAF-XC886LM-6FFA(5v)@QFP48 [DX3007]
SAF-XC886LM-6FFI(3.3v)@QFP48 [DX3007]
SAF-XC886LM-6FFI(5v)@QFP48 [DX3007]
SAF-XC886LM-8FFA(3.3v)@QFP48 [DX3007]
SAF-XC886LM-8FFA(5v)@QFP48 [DX3007]
SAF-XC886LM-8FFI(3.3v)@QFP48 [DX3007]
SAF-XC886LM-8FFI(5v)@QFP48 [DX3007]
SAF-XC888-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888-6FFA(5v)@QFP64 [DX3011]
SAF-XC888-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888-6FFI(5v)@QFP64 [DX3011]
SAF-XC888-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888-8FFA(5v)@QFP64 [DX3011]
SAF-XC888-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888-8FFI(5v)@QFP64 [DX3011]
SAF-XC888C-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888C-6FFA(5v)@QFP64 [DX3011]
SAF-XC888C-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888C-6FFI(5v)@QFP64 [DX3011]

SAF-XC888C-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888C-8FFA(5v)@QFP64 [DX3011]
SAF-XC888C-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888C-8FFI(5v)@QFP64 [DX3011]
SAF-XC888CLM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888CLM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888CLM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888CLM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CLM-8FFI(5v)@QFP64 [DX3011]
SAF-XC888CM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888CM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888CM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888CM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888CM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888CM-8FFI(5v)@QFP64 [DX3011]
SAF-XC888LM-6FFA(3.3v)@QFP64 [DX3011]
SAF-XC888LM-6FFA(5v)@QFP64 [DX3011]
SAF-XC888LM-6FFI(3.3v)@QFP64 [DX3011]
SAF-XC888LM-6FFI(5v)@QFP64 [DX3011]
SAF-XC888LM-8FFA(3.3v)@QFP64 [DX3011]
SAF-XC888LM-8FFA(5v)@QFP64 [DX3011]
SAF-XC888LM-8FFI(3.3v)@QFP64 [DX3011]
SAF-XC888LM-8FFI(5v)@QFP64 [DX3011]
SAF-XE160FU-4FXR@TSSOP38 [DX1012]
SAF-XE160FU-8FXR@TSSOP38 [DX1012]
SAF-XE161FL-12FXV@QFN48 [DX4021]　　SAF-XE161FL-20FXV@QFN48 [DX4021]
SAF-XE161FU-4FXV@QFN48 [DX4021]　　SAF-XE161FU-8FXV@QFN48 [DX4021]
SAF-XE161HL-12FXV@QFN48 [DX4021]　　SAF-XE161HL-20FXV@QFN48 [DX4021]
SAF-XE162FL-12F66L@QFP64 [DX3011]
SAF-XE162FL-20F66L@QFP64 [DX3011]
SAF-XE162HL-12F66L@QFP64 [DX3011]
SAF-XE162HL-20F66L@QFP64 [DX3011]
SAF-XE164F-24F66L@QFP100 [DX3043]
SAF-XE164F-48F66L@QFP100 [DX3043]
SAF-XE164F-72F66L@QFP100 [DX3043]
SAF-XE164F-96F66L@QFP100 [DX3043]
SAF-XE164FM-24F80L@QFP100 [DX3043]
SAF-XE164FM-48F80L@QFP100 [DX3043]
SAF-XE164FM-72F80L@QFP100 [DX3043]
SAF-XE164FN-24F80L@QFP100 [DX3043]
SAF-XE164FN-40F80L@QFP100 [DX3043]
SAF-XE164G-24F66L@QFP100 [DX3043]
SAF-XE164G-48F66L@QFP100 [DX3043]

SAF-XE164G-72F66L@QFP100 [DX3043]
SAF-XE164G-96F66L@QFP100 [DX3043]
SAF-XE164GM-24F80L@QFP100 [DX3043]
SAF-XE164GM-48F80L@QFP100 [DX3043]
SAF-XE164GM-72F80L@QFP100 [DX3043]
SAF-XE164GN-24F80L@QFP100 [DX3043]
SAF-XE164GN-40F80L@QFP100 [DX3043]
SAF-XE164H-24F66L@QFP100 [DX3043]
SAF-XE164H-48F66L@QFP100 [DX3043]
SAF-XE164H-72F66L@QFP100 [DX3043]
SAF-XE164H-96F66L@QFP100 [DX3043]
SAF-XE164HM-24F80L@QFP100 [DX3043]
SAF-XE164HM-48F80L@QFP100 [DX3043]
SAF-XE164HM-72F80L@QFP100 [DX3043]
SAF-XE164HN-24F80L@QFP100 [DX3043]
SAF-XE164HN-40F80L@QFP100 [DX3043]
SAF-XE164K-24F66L@QFP100 [DX3043]
SAF-XE164K-48F66L@QFP100 [DX3043]
SAF-XE164K-72F66L@QFP100 [DX3043]
SAF-XE164K-96F66L@QFP100 [DX3043]
SAF-XE164KM-24F80L@QFP100 [DX3043]
SAF-XE164KM-48F80L@QFP100 [DX3043]
SAF-XE164KM-72F80L@QFP100 [DX3043]
SAF-XE164KN-24F80L@QFP100 [DX3043]
SAF-XE164KN-40F80L@QFP100 [DX3043]
SAF-XE167F-48F66L@TQFP144 [DX3035]
SAF-XE167F-72F66L@TQFP144 [DX3035]
SAF-XE167F-96F66L@TQFP144 [DX3035]
SAF-XE167G-48F66L@TQFP144 [DX3035]
SAF-XE167G-72F66L@TQFP144 [DX3035]
SAF-XE167G-96F66L@TQFP144 [DX3035]
SAF-XE167H-48F66L@TQFP144 [DX3035]
SAF-XE167H-72F66L@TQFP144 [DX3035]
SAF-XE167H-96F66L@TQFP144 [DX3035]
SAF-XE167K-48F66L@TQFP144 [DX3035]
SAF-XE167K-72F66L@TQFP144 [DX3035]
SAF-XE167K-96F66L@TQFP144 [DX3035]
SAF-XE169FH-136FXL [DX3103]
SAF-XE169FH-200FXL [DX3103]
SAH-C504-2EM@TQFP44 [DX3002]
SAH-C505A-4EM@TQFP44 [DX3002]
SAH-C505CA-4EM@TQFP44 [DX3002]
SAK-C164CI-8EM@TQFP80 [DX3018]
SAK-C504-2EM@TQFP44 [DX3002]
SAK-C505A-4EM@TQFP44 [DX3002]
SAK-C505CA-4EM@TQFP44 [DX3002]
SAK-C505L-4EM@PQFP80 [DX3018]
SAK-C515C-8EM@TQFP80 [DX3018]
SAK-XC161CJ-16F20F@TQFP144 [DX3035]
SAK-XC161CJ-16F40F@TQFP144 [DX3035]
SAK-XC164CM-16F20F@TQFP64 [DX3011]
SAK-XC164CM-16F40F@TQFP64 [DX3011]
SAK-XC164CM-4F20F@TQFP64 [DX3011]

SAK-XC164CM-4F40F@TQFP64 [DX3011]
SAK-XC164CM-8F20F@TQFP64 [DX3011]
SAK-XC164CM-8F40F@TQFP64 [DX3011]
SAK-XC164CS-16F20F@TQFP100 [DX3021]
SAK-XC164CS-16F40F@TQFP100 [DX3021]
SAK-XC164CS-32F20F@TQFP100 [DX3021]
SAK-XC164CS-32F40F@TQFP100 [DX3021]
SAK-XC164CS-8F20F@TQFP100 [DX3021]
SAK-XC164CS-8F40F@TQFP100 [DX3021]
SAK-XC167CI-16F20F@TQFP144 [DX3035]
SAK-XC167CI-16F40F@TQFP144 [DX3035]
SAK-XC2210U-4FXRTSSOP38 [DX1012] SAK-XC2210U-8FXRTSSOP38 [DX1012]
SAK-XC2220L-12FXV@QFN48 [DX4021] SAK-XC2220L-20FXV@QFN48 [DX4021]
SAK-XC2220U-4FXV@QFN48 [DX4021] SAK-XC2220U-8FXV@QFN48 [DX4021]
SAK-XC2224L-12FXV@QFN48 [DX4021] SAK-XC2224L-20FXV@QFN48 [DX4021]
SAK-XC2230L-12F66L@QFP64 [DX3011]
SAK-XC2230L-20F66L@QFP64 [DX3011]
SAK-XC2234L-12F66L@QFP64 [DX3011]
SAK-XC2234L-20F66L@QFP64 [DX3011]
SAK-XC2261N-16F40L@QFP100 [DX3043]
SAK-XC2261N-16F80L@QFP100 [DX3043]
SAK-XC2261N-24F40L@QFP100 [DX3043]
SAK-XC2261N-24F80L@QFP100 [DX3043]
SAK-XC2263M-104F80L@TQFP100 [DX3043]
SAK-XC2263M-56F80L@QFP100 [DX3043]
SAK-XC2263M-72F80L@QFP100 [DX3043]
SAK-XC2263N-16F40L@QFP100 [DX3043]
SAK-XC2263N-16F80L@QFP100 [DX3043]
SAK-XC2263N-24F40L@QFP100 [DX3043]
SAK-XC2263N-24F80L@QFP100 [DX3043]
SAK-XC2263N-40F40L@QFP100 [DX3043]
SAK-XC2263N-40F80L@QFP100 [DX3043]
SAK-XC2264M-104F80L@TQFP100 [DX3043]
SAK-XC2264M-56F80L@QFP100 [DX3043]
SAK-XC2264M-72F80L@QFP100 [DX3043]
SAK-XC2264N-16F40L@QFP100 [DX3043]
SAK-XC2264N-16F80L@QFP100 [DX3043]
SAK-XC2264N-24F40L@QFP100 [DX3043]
SAK-XC2264N-24F80L@QFP100 [DX3043]
SAK-XC2264N-40F40L@QFP100 [DX3043]
SAK-XC2264N-40F80L@QFP100 [DX3043]
SAK-XC2265M-104F80L@TQFP100 [DX3043]
SAK-XC2265M-56F80L@QFP100 [DX3043]
SAK-XC2265M-72F80L@QFP100 [DX3043]
SAK-XC2265N-16F40L@QFP100 [DX3043]
SAK-XC2265N-16F80L@QFP100 [DX3043]
SAK-XC2265N-24F40L@QFP100 [DX3043]
SAK-XC2265N-24F80L@QFP100 [DX3043]

SAK-XC2265N-40F40L@QFP100 [DX3043]
SAK-XC2265N-40F80L@QFP100 [DX3043]
SAK-XC2267M-104F80L@TQFP100 [DX3043]
SAK-XC2267M-56F80L@QFP100 [DX3043]
SAK-XC2267M-72F80L@QFP100 [DX3043]
SAK-XC2268M-104F80L@TQFP100 [DX3043]
SAK-XC2268M-56F80L@QFP100 [DX3043]
SAK-XC2268M-72F80L@QFP100 [DX3043]
SAK-XC2268N-16F40L@QFP100 [DX3043]
SAK-XC2268N-16F80L@QFP100 [DX3043]
SAK-XC2268N-24F40L@QFP100 [DX3043]
SAK-XC2268N-24F80L@QFP100 [DX3043]
SAK-XC2268N-40F40L@QFP100 [DX3043]
SAK-XC2268N-40F80L@QFP100 [DX3043]
SAK-XC2285-72F66L@TQFP144 [DX3035]
SAK-XC2285-96F66L@TQFP144 [DX3035]
SAK-XC2286-72F66L@TQFP144 [DX3035]
SAK-XC2286-96F66L@TQFP144 [DX3035]
SAK-XC2287-72F66L@TQFP144 [DX3035]
SAK-XC2287-96F66L@TQFP144 [DX3035]
SAK-XC2336B-24F66L@QFP64 [DX3011]
SAK-XC2336B-40F66L@QFP64 [DX3011]
SAK-XC2361B-24F80L@QFP100 [DX3043]
SAK-XC2361B-40F80L@QFP100 [DX3043]
SAK-XC2363B-24F80L@QFP100 [DX3043]
SAK-XC2363B-40F80L@QFP100 [DX3043]
SAK-XC2364B-24F80L@QFP100 [DX3043]
SAK-XC2364B-40F80L@QFP100 [DX3043]
SAK-XC2365B-24F80L@QFP100 [DX3043]
SAK-XC2365B-40F80L@QFP100 [DX3043]
SAK-XC2387-72F66L@TQFP144 [DX3035]
SAK-XC2734X-40F80L@QFP64 [DX3011]
SAK-XC2764X-40F80L@QFP100 [DX3043]
SAK-XC824M-1FGI@SOIC20 [DX1033] SAK-XC846-1FR@TSSOP38 [DX1012]
SAK-XC866-1FR@TSSOP38 [DX1012]
SAK-XC866-2FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866-2FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866-4FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866-4FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866L-2FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866L-2FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC866L-4FR(A STEP)@TSSOP38 [DX1012]
SAK-XC866L-4FR(BB STEP)@TSSOP38 [DX1012]
SAK-XC886-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886-6FFA(5v)@QFP48 [DX3007]
SAK-XC886-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886-6FFI(5v)@QFP48 [DX3007]
SAK-XC886-8FFA(3.3v)@QFP48 [DX3007]

SAK-XC886-8FFA(5v)@QFP48 [DX3007]
SAK-XC886-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886-8FFI(5v)@QFP48 [DX3007]
SAK-XC886C-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886C-6FFA(5v)@QFP48 [DX3007]
SAK-XC886C-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886C-6FFI(5v)@QFP48 [DX3007]
SAK-XC886C-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886C-8FFA(5v)@QFP48 [DX3007]
SAK-XC886C-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886C-8FFI(5v)@QFP48 [DX3007]
SAK-XC886CLM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886CLM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886CLM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886CLM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CLM-8FFI(5v)@QFP48 [DX3007]
SAK-XC886CM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886CM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886CM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886CM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886CM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886CM-8FFI(5v)@QFP48 [DX3007]
SAK-XC886LM-6FFA(3.3v)@QFP48 [DX3007]
SAK-XC886LM-6FFA(5v)@QFP48 [DX3007]
SAK-XC886LM-6FFI(3.3v)@QFP48 [DX3007]
SAK-XC886LM-6FFI(5v)@QFP48 [DX3007]
SAK-XC886LM-8FFA(3.3v)@QFP48 [DX3007]
SAK-XC886LM-8FFA(5v)@QFP48 [DX3007]
SAK-XC886LM-8FFI(3.3v)@QFP48 [DX3007]
SAK-XC886LM-8FFI(5v)@QFP48 [DX3007]
SAK-XC888-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888-6FFA(5v)@QFP64 [DX3011]
SAK-XC888-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888-6FFI(5v)@QFP64 [DX3011]
SAK-XC888-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888-8FFA(5v)@QFP64 [DX3011]
SAK-XC888-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888-8FFI(5v)@QFP64 [DX3011]
SAK-XC888C-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888C-6FFA(5v)@QFP64 [DX3011]
SAK-XC888C-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888C-6FFI(5v)@QFP64 [DX3011]
SAK-XC888C-8FFA(3.3v)@QFP64 [DX3011]

SAK-XC888C-8FFA(5v)@QFP64 [DX3011]
SAK-XC888C-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888C-8FFI(5v)@QFP64 [DX3011]
SAK-XC888CLM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888CLM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888CLM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888CLM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CLM-8FFI(5v)@QFP64 [DX3011]
SAK-XC888CM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888CM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888CM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888CM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888CM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888CM-8FFI(5v)@QFP64 [DX3011]
SAK-XC888LM-6FFA(3.3v)@QFP64 [DX3011]
SAK-XC888LM-6FFA(5v)@QFP64 [DX3011]
SAK-XC888LM-6FFI(3.3v)@QFP64 [DX3011]
SAK-XC888LM-6FFI(5v)@QFP64 [DX3011]
SAK-XC888LM-8FFA(3.3v)@QFP64 [DX3011]
SAK-XC888LM-8FFA(5v)@QFP64 [DX3011]
SAK-XC888LM-8FFI(3.3v)@QFP64 [DX3011]
SAK-XC888LM-8FFI(5v)@QFP64 [DX3011]
SAK-XE160FU-4FXR@TSSOP38 [DX1012]
SAK-XE160FU-8FXR@TSSOP38 [DX1012]
SAK-XE161FL-12FXV@QFN48 [DX4021]　　SAK-XE161FL-20FXV@QFN48 [DX4021]
SAK-XE161FU-4FXV@QFN48 [DX4021]　　SAK-XE161FU-8FXV@QFN48 [DX4021]
SAK-XE161HL-12FXV@QFN48 [DX4021]　　SAK-XE161HL-20FXV@QFN48 [DX4021]
SAK-XE162FL-12F66L@QFP64 [DX3011]
SAK-XE162FL-20F66L@QFP64 [DX3011]
SAK-XE162HL-12F66L@QFP64 [DX3011]
SAK-XE162HL-20F66L@QFP64 [DX3011]
SAK-XE164FM-24F80L@QFP100 [DX3043]
SAK-XE164FM-48F80L@QFP100 [DX3043]
SAK-XE164FM-72F80L@QFP100 [DX3043]
SAK-XE164FN-24F80L@QFP100 [DX3043]
SAK-XE164FN-40F80L@QFP100 [DX3043]
SAK-XE164GM-24F80L@QFP100 [DX3043]
SAK-XE164GM-48F80L@QFP100 [DX3043]
SAK-XE164GM-72F80L@QFP100 [DX3043]
SAK-XE164GN-24F80L@QFP100 [DX3043]
SAK-XE164GN-40F80L@QFP100 [DX3043]
SAK-XE164HM-24F80L@QFP100 [DX3043]
SAK-XE164HM-48F80L@QFP100 [DX3043]

SAK-XE164HM-72F80L@QFP100 [DX3043]
SAK-XE164HN-24F80L@QFP100 [DX3043]
SAK-XE164HN-40F80L@QFP100 [DX3043]
SAK-XE164KM-24F80L@QFP100 [DX3043]
SAK-XE164KM-48F80L@QFP100 [DX3043]
SAK-XE164KM-72F80L@QFP100 [DX3043]
SAK-XE164KN-24F80L@QFP100 [DX3043]
SAK-XE164KN-40F80L@QFP100 [DX3043]
SAK-XE169FH-136FXL [DX3103]
SAK-XE169FH-200FXL [DX3103]
SAX-XC824M-1FGI@SOIC20 [DX1033]
SAX-XC878-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878-13FFA(5v)@QFP64 [DX3011]
SAX-XC878-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878-16FFA(5v)@QFP64 [DX3011]
SAX-XC878C-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878C-13FFA(5v)@QFP64 [DX3011]
SAX-XC878C-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878C-16FFA(5v)@QFP64 [DX3011]
SAX-XC878CM-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878CM-13FFA(5v)@QFP64 [DX3011]
SAX-XC878CM-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878CM-16FFA(5v)@QFP64 [DX3011]
SAX-XC878L-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878L-13FFA(5v)@QFP64 [DX3011]
SAX-XC878L-16FFA(3.3v)@QFP64 [DX3011]
SAX-XC878L-16FFA(5v)@QFP64 [DX3011]
SAX-XC878LM-13FFA(3.3v)@QFP64 [DX3011]
SAX-XC878LM-13FFA(5v)@QFP64 [DX3011]
XMC1100-T016F0008 [DX1000]
XMC1100-T016F0016 [DX1000]
XMC1100-T016F0064 [DX1000]
XMC1100-T038F0016 [DX1012]
XMC1100-T038F0032 [DX1012]
XMC1100-T038F0064 [DX1012]
XMC1201-T038F0016 [DX1012]
XMC1201-T038F0032 [DX1012]
XMC1201-T038F0064 [DX1012]
XMC1201-T038F0200 [DX1012]
XMC1202-T016X0016 [DX1000]
XMC1202-T016X0032 [DX1000]
XMC1202-T028X0016 [DX1001]
XMC1202-T028X0032 [DX1001]
XMC1301-T016F0008 [DX1000]
XMC1301-T016F0016 [DX1000]
XMC1301-T038F0008 [DX1012]
XMC1301-T038F0016 [DX1012]
XMC1301-T038F0032 [DX1012]
XMC1301-T038F0064 [DX1012]
XMC1302-T038X0016 [DX1012]
XMC1302-T038X0032 [DX1012]
XMC1302-T038X0064 [DX1012]
XMC1302-T038X0200 [DX1012]
XMC4100-F64F128 [DX3011]
XMC4100-F64K128 [DX3011]
XMC4100-Q48F128 [DX4021]
XMC4100-Q48K128 [DX4021]
XMC4104-F64F128 [DX3011]
XMC4104-F64F64 [DX3011]
XMC4104-F64K128 [DX3011]
XMC4104-F64K64 [DX3011]
XMC4104-Q48F128 [DX4021]
XMC4104-Q48F64 [DX4021]
XMC4104-Q48K128 [DX4021]
XMC4104-Q48K64 [DX4021]
XMC4200-F64F256 [DX3011]
XMC4200-F64K256 [DX3011]
XMC4200-Q48F256 [DX4021]
XMC4200-Q48K256 [DX4021]

XMC4400-F100F256 [DX3021]
XMC4400-F100K256 [DX3021]
XMC4400-F64F256 [DX3011]
XMC4400-F64K256 [DX3011]
XMC4402-F100F256 [DX3021]
XMC4402-F64F256 [DX3011]
XMC4500-F100F1024 [DX3021]
XMC4500-F100K1024 [DX3021]
XMC4500-F144F1024 [DX3035]
XMC4500-F144K1024 [DX3035]
XMC4502-F100F768 [DX3021]
XMC4504-F100F512 [DX3021]
XMC4504-F144F512 [DX3035]
XMC4400-F100F512 [DX3021]
XMC4400-F100K512 [DX3021]
XMC4400-F64F512 [DX3011]
XMC4400-F64K512 [DX3011]
XMC4402-F100K256 [DX3021]
XMC4402-F64K256 [DX3011]
XMC4500-F100F768 [DX3021]
XMC4500-F100K768 [DX3021]
XMC4500-F144F768 [DX3035]
XMC4500-F144K768 [DX3035]
XMC4502-F100K768 [DX3021]
XMC4504-F100K512 [DX3021]
XMC4504-F144K512 [DX3035]

SIERRA

E(E)PROM/FRAM/NVRAM

SC22101CM [DX1033]
SC22201CM [DX1033]
SC22101CN [DX0001]
SC22201CN [DX0001]

SIGNETICS

E(E)PROM/FRAM/NVRAM

27C010 [DX0001]
27C010@TSOP32 [DX1002]
27C040@PLCC32 [DX2032]
27C210 [DX0001]
27C240 [DX0001]
27C256 [DX0001]
27C512 [DX0001]
27C64A [DX0001]
27HC641 [DX0001]
27HC642 [DX0001]
PCA8582A [DX0001]
PCA8582B [DX0001]
PCA8582C [DX0001]
PCA8582D [DX0001]
PCA8582E [DX0001]
PCD8582A [DX0001]
PCD8582B [DX0001]
PCD8582C [DX0001]
PCD8582D [DX0001]
PCD8582E [DX0001]
PCF8582A [DX0001]
27C010@PLCC32 [DX2032]
27C040 [DX0001]
27C040@TSOP32 [DX1002]
27C210@PLCC44 [DX2044]
27C240@PLCC44 [DX2044]
27C256@PLCC32 [DX2032]
27C512@PLCC32 [DX2032]
27C64A@PLCC32 [DX2032]
27HC641@PLCC28 [DX2028]
27HC642@PLCC28 [DX2028]
PCA8582A@SOIC8 [DX1045]
PCA8582B@SOIC8 [DX1045]
PCA8582C@SOIC8 [DX1045]
PCA8582D@SOIC8 [DX1045]
PCA8582E@SOIC8 [DX1045]
PCD8582A@SOIC8 [DX1045]
PCD8582B@SOIC8 [DX1045]
PCD8582C@SOIC8 [DX1045]
PCD8582D@SOIC8 [DX1045]
PCD8582E@SOIC8 [DX1045]
PCF8582A@SOIC8 [DX1045]

PCF8582B [DX0001]
PCF8582C [DX0001]
PCF8582D [DX0001]
PCF8582E [DX0001]
PCF8594 [DX0001]
PCF8594C [DX0001]
PCF8594D [DX0001]
PCF8594E [DX0001]
PCF8598 [DX0001]
PCF8598C [DX0001]
PCF8598D [DX0001]
PCF8598E [DX0001]
PCF8582B@SOIC8 [DX1045]
PCF8582C@SOIC8 [DX1045]
PCF8582D@SOIC8 [DX1045]
PCF8582E@SOIC8 [DX1045]
PCF8594@SOIC8 [DX1045]
PCF8594C@SOIC8 [DX1045]
PCF8594D@SOIC8 [DX1045]
PCF8594E@SOIC8 [DX1045]
PCF8598@SOIC8 [DX1044]
PCF8598C@SOIC8 [DX1044]
PCF8598D@SOIC8 [DX1044]
PCF8598E@SOIC8 [DX1044]

BPROM

82LS135 [DX0001]
82S123 [DX0001]
82S126 [DX0001]
82S129 [DX0001]
82S130 [DX0001]
82S131 [DX0001]
82S135 [DX0001]
82S136 [DX0001]
82S137A [DX0001]
82S137C [DX0001]
82S141 [DX0001]
82S146@PLCC20 [DX2020]
82S147@PLCC20 [DX2020]
82S147A@PLCC20 [DX2020]
82S147B@PLCC20 [DX2020]
82S191 [DX0001]
82S191B [DX0001]
82S23 [DX0001]
82LS135@PLCC20 [DX2020]
82S123A [DX0001]
82S126A [DX0001]
82S129A [DX0001]
82S130A [DX0001]
82S131A [DX0001]
82S135@PLCC20 [DX2020]
82S137 [DX0001]
82S137B [DX0001]
82S140 [DX0001]
82S146 [DX0001]
82S147 [DX0001]
82S147A [DX0001]
82S147B [DX0001]
82S167 [DX0001]
82S191A [DX0001]
82S191C [DX0001]
82S23A [DX0001]

PLD

82S105 [DX0001]
82S152 [DX0001]
82S153 [DX0001]
82S155 [DX0001]
82S157 [DX0001]
82S159 [DX0001]
82S167 [DX0001]
82S168 [DX0001]
82S173 [DX0001]
82S179 [DX0001]
82S105@PLCC28 [DX2028]
82S152@PLCC20 [DX2020]
82S153@PLCC20 [DX2020]
82S155@PLCC20 [DX2020]
82S157@PLCC20 [DX2020]
82S159@PLCC20 [DX2020]
82S167@PLCC28 [DX2028]
82S168@PLCC28 [DX2028]
82S173@PLCC28 [DX2028]
82S179@PLCC28 [DX2028]

PLS104 [DX0001]
PLS104A [DX0001]
PLS105 [DX0001]
PLS105A [DX0001]
PLS152 [DX0001]
PLS153 [DX0001]
PLS153A [DX0001]
PLS155 [DX0001]
PLS157 [DX0001]
PLS159 [DX0001]
PLS159A [DX0001]
PLS167 [DX0001]
PLS167A [DX0001]
PLS168 [DX0001]
PLS168A [DX0001]
PLS173 [DX0001]
PLS179 [DX0001]
PLS104@PLCC28 [DX2028]
PLS104A@PLCC28 [DX2028]
PLS105@PLCC28 [DX2028]
PLS105A@PLCC28 [DX2028]
PLS152@PLCC20 [DX2020]
PLS153@PLCC20 [DX2020]
PLS153A@PLCC20 [DX2020]
PLS155@PLCC20 [DX2020]
PLS157@PLCC20 [DX2020]
PLS159@PLCC20 [DX2020]
PLS159A@PLCC20 [DX0001]
PLS167@PLCC28 [DX2028]
PLS167A@PLCC28 [DX2028]
PLS168@PLCC28 [DX2028]
PLS168A@PLCC28 [DX2028]
PLS173@PLCC28 [DX2028]
PLS179@PLCC28 [DX2028]

MICROCONTROLLER

PSD301@PLCC44 [DX2044]
PSD302@PLCC44 [DX2044]
PSD303@PLCC44 [DX2044]
PSD311@PLCC44 [DX2044]
PSD312@PLCC44 [DX2044]
PSD313@PLCC44 [DX2044]
PSD313-B@PLCC44 [DX2044]
PSD313L@PLCC44 [DX2044]
S87C054@SDIP42 [DX0042]
S87C451@PLCC68 [DX2068]
S87C453@PLCC68 [DX2068]
S87C51@PLCC44 [DX2044]
S87C51FA [DX0001]
S87C51FA@TQFP44 [DX3002]
S87C51FB@PLCC44 [DX2044]
S87C51FC [DX0001]
S87C51FC@TQFP44 [DX3003]
S87C52@PLCC44 [DX2044]
S87C524 [DX0001]
S87C524@TQFP44 [DX3003]
S87C528@PLCC44 [DX2044]
S87C54 [DX0001]
S87C54@TQFP44 [DX3002]
S87C550@PLCC44 [DX2044]
S87C552@PQFP80 [DX3019]
S87C554@PQFP80 [DX3019]
S87C575@PLCC44 [DX2044]
PSD301L@PLCC44 [DX2044]
PSD302L@PLCC44 [DX2044]
PSD303L@PLCC44 [DX2044]
PSD311L@PLCC44 [DX2044]
PSD312L@PLCC44 [DX2044]
PSD313@TQFP44 [DX3003]
PSD313-B@TQFP44 [DX3003]
PSD313L@TQFP44 [DX3003]
S87C055@SDIP42 [DX0042]
S87C451@SDIP64 [DX0064]
S87C51 [DX0001]
S87C51@TQFP44 [DX3002]
S87C51FA@PLCC44 [DX2044]
S87C51FB [DX0001]
S87C51FB@TQFP44 [DX3002]
S87C51FC@PLCC44 [DX2044]
S87C52 [DX0001]
S87C52@TQFP44 [DX3002]
S87C524@PLCC44 [DX2044]
S87C528 [DX0001]
S87C528@TQFP44 [DX3003]
S87C54@PLCC44 [DX2044]
S87C550 [DX0001]
S87C552@PLCC68 [DX2068]
S87C554@PLCC68 [DX2068]
S87C575 [DX0001]
S87C575@TQFP44 [DX3002]

S87C576 [DX0001]
S87C576@PLCC44 [DX2044]
S87C576@TQFP44 [DX3002]
S87C58 [DX0001]
S87C58@PLCC44 [DX2044]
S87C58@TQFP44 [DX3002]
S87C591@PLCC44 [DX2044]
S87C591@TQFP44 [DX3002]
S87C592@PLCC68 [DX2068]
S87C652 [DX0001]
S87C652@PLCC44 [DX2044]
S87C652@TQFP44 [DX3002]
S87C654 [DX0001]
S87C654@PLCC44 [DX2044]
S87C654@TQFP44 [DX3002]
S87C748 [DX0001]
S87C748@PLCC28 [DX2028]
S87C749 [DX0001]
S87C749@PLCC28 [DX2028]
S87C750 [DX0001]
S87C750@PLCC28 [DX2028]
S87C750@SSOP24 [DX1026]
S87C751 [DX0001]
S87C751@PLCC28 [DX2028]
S87C751@SSOP24 [DX1026]
S87C752 [DX0001]
S87C752@PLCC28 [DX2028]
S87C752@SSOP28 [DX1026]
S87C754 [DX0001]
S87C754@PLCC28 [DX2028]
S87C754@SSOP28 [DX1026]
S87L51FA [DX0001]
S87L51FA@PLCC44 [DX2044]
S87L51FA@TQFP44 [DX3002]
S87L51FB [DX0001]
S87L51FB@PLCC44 [DX2044]
S87L51FB@TQFP44 [DX3002]

Silan

MICROCONTROLLER

SC51P1816LL@TQFP48 [DX3007]

SILICON

MICROCONTROLLER

C8051F388-GQ [DX3007]
C8051F389-GM [DX4015]
C8051F389-GQ [DX3001]
C8051F38A-GQ [DX3007]
C8051F38B-GM [DX4015]
C8051F38B-GQ [DX3001]
C8051F970-A-GM [DX4043]
C8051F970-GM [DX4043]
C8051F971-A-GM [DX4015]
C8051F971-GM [DX4015]
C8051F972-A-GM [DX4012]
C8051F972-GM [DX4012]
C8051F973-A-GM [DX4043]
C8051F973-GM [DX4043]
C8051F974-A-GM [DX4015]
C8051F974-GM [DX4015]
C8051F975-A-GM [DX4012]
C8051F975-GM [DX4012]
C8051T320-B-GQ [DX3001]
C8051T321-B-GM [DX4013]
C8051T322-B-GQ [DX3001]
C8051T323-B-GM [DX4013]
C8051T326-B-GM [DX4013]
C8051T327-B-GM [DX4013]
C8051T620-B-GM [DX4015]
C8051T621-B-GM [DX4015]
C8051T622-B-GM [DX4012]
C8051T623-B-GM [DX4012]
EM351@QFN48 [DX4021]
EM357@QFN48 [DX4021]

Silicon Laboratories

MICROCONTROLLER

C8051F000@TQFP64 [DX3011]
C8051F001@TQFP48 [DX3007]
C8051F002@TQFP32 [DX3001]
C8051F005@TQFP64 [DX3011]
C8051F006@TQFP48 [DX3007]
C8051F007@TQFP32 [DX3001]
C8051F010@TQFP64 [DX3011]
C8051F011@TQFP48 [DX3007]
C8051F012@TQFP32 [DX3001]
C8051F015@TQFP64 [DX3011]
C8051F016@TQFP48 [DX3007]
C8051F017@TQFP32 [DX3001]
C8051F018@TQFP64
C8051F019@TQFP48
C8051F020@TQFP100 [DX3021]
C8051F020JTAG [DX0001]
C8051F021@TQFP64 [DX3011]
C8051F021JTAG [DX0001]
C8051F022@TQFP100 [DX3021]
C8051F022JTAG [DX0001]
C8051F023@TQFP64 [DX3011]
C8051F023JTAG [DX0001]
C8051F040@TQFP100 [DX3021]
C8051F040JTAG [DX0001]
C8051F041@TQFP64 [DX3011]
C8051F041JTAG [DX0001]
C8051F042@TQFP100 [DX3021]
C8051F042JTAG [DX0001]
C8051F043@TQFP64 [DX3011]
C8051F043JTAG [DX0001]
C8051F044@TQFP100 [DX3021]
C8051F044JTAG [DX0001]
C8051F045@TQFP64 [DX3011]
C8051F045JTAG [DX0001]
C8051F046@TQFP100 [DX3021]
C8051F046JTAG [DX0001]
C8051F047@TQFP64 [DX3011]
C8051F047JTAG [DX0001]
C8051F060@TQFP100 [DX3021]
C8051F061@TQFP64 [DX3011]
C8051F062@TQFP100 [DX3021]
C8051F063@TQFP64 [DX3011]
C8051F064@TQFP100 [DX3021]
C8051F065@TQFP64 [DX3011]
C8051F066@TQFP100 [DX3021]
C8051F067@TQFP64 [DX3011]
C8051F120*ISP [DX0001]
C8051F120@TQFP100 [DX3021]
C8051F120-GQ*ISP [DX0001]
C8051F120-GQ@TQFP100 [DX3021]
C8051F121*ISP [DX0001]
C8051F121@TQFP64 [DX3011]
C8051F121-GQ*ISP [DX0001]
C8051F121-GQ@TQFP64 [DX3011]
C8051F122*ISP [DX0001]
C8051F122@TQFP100 [DX3021]
C8051F122-GQ*ISP [DX0001]
C8051F122-GQ@TQFP100 [DX3021]
C8051F123*ISP [DX0001]
C8051F123@TQFP64 [DX3011]
C8051F123-GQ*ISP [DX0001]
C8051F123-GQ@TQFP64 [DX3011]
C8051F124*ISP [DX0001]
C8051F124@TQFP100 [DX3021]
C8051F124-GQ*ISP [DX0001]
C8051F124-GQ@TQFP100 [DX3021]
C8051F125*ISP [DX0001]
C8051F125@TQFP64 [DX3011]
C8051F125-GQ*ISP [DX0001]
C8051F125-GQ@TQFP64 [DX3011]
C8051F126*ISP [DX0001]
C8051F126@TQFP100 [DX3021]
C8051F126-GQ*ISP [DX0001]
C8051F126-GQ@TQFP100 [DX3021]
C8051F127*ISP [DX0001]
C8051F127@TQFP64 [DX3011]
C8051F127-GQ*ISP [DX0001]
C8051F127-GQ@TQFP64 [DX3011]
C8051F130*ISP [DX0001]
C8051F130@TQFP100 [DX3021]
C8051F130-GQ*ISP [DX0001]
C8051F130-GQ@TQFP100 [DX3021]
C8051F131*ISP [DX0001]
C8051F131@TQFP64 [DX3011]
C8051F131-GQ*ISP [DX0001]
C8051F131-GQ@TQFP64 [DX3011]

C8051F132*ISP [DX0001]
C8051F132-GQ*ISP [DX0001]
C8051F133*ISP [DX0001]
C8051F133-GQ*ISP [DX0001]
C8051F206@TQFP48 [DX3007]
C8051F221@TQFP32 [DX3001]
C8051F230@TQFP48 [DX3007]
C8051F236@TQFP48 [DX3007]
C8051F300-GM@QFN11 [DX4007]
C8051F301@QFN11 [DX4007]
C8051F301-GS@SOIC14 [DX1016]
C8051F302-GM@QFN11 [DX4007]
C8051F303@QFN11 [DX4007]
C8051F303-GS [DX1016]
C8051F304-GM@QFN11 [DX4007]
C8051F305@QFN11 [DX4007]
C8051F305-GS [DX1016]
C8051F310A@TQFP32 [DX3001]
C8051F310-GQ@TQFP32 [DX3001]
C8051F311-GM@QFN28 [DX4013]
C8051F312-GQ@TQFP32 [DX3001]
C8051F313-GM@QFN28 [DX4013]
C8051F314-GQ@TQFP32 [DX3001]
C8051F315-GM@QFN28 [DX4013]
C8051F317-GM@QFN24 [DX4012]
C8051F320A@TQFP32 [DX3001]
C8051F320-GQ@TQFP32 [DX3001]
C8051F321@QFN28(Left Down) [DX4013]
C8051F321A@QFN28 [DX4013]
C8051F321A@QFN28(Left Down) [DX4013]
C8051F321A-GM@QFN28 [DX4013]
C8051F321A-GM@QFN28(Left Down) [DX4013]
C8051F321-GM@QFN28 [DX4013]
C8051F321-GM@QFN28(Left Down) [DX4013]
C8051F326@QFN28 [DX4013]
C8051F326-GQ@QFN28 [DX4013]
C8051F327-GM@QFN28 [DX4013]
C8051F330@MLP20 [DX4011]
C8051F330-GM@MLP20 [DX4011]
C8051F331@MLP20 [DX4011]
C8051F332@MLP20 [DX4011]
C8051F333@MLP20 [DX4011]
C8051F334@MLP20 [DX4011]
C8051F335@MLP20 [DX4011]
C8051F336@MLP20 [DX4011]
C8051F337@MLP20 [DX4011]
C8051F338@MLP24 [DX4012]
C8051F339@MLP24 [DX4012]
C8051F132@TQFP100 [DX3021]
C8051F132-GQ@TQFP100 [DX3021]
C8051F133@TQFP64 [DX3011]
C8051F133-GQ@TQFP64 [DX3011]
C8051F220@TQFP48 [DX3007]
C8051F226@TQFP48 [DX3007]
C8051F231@TQFP32 [DX3001]
C8051F300@QFN11 [DX4007]
C8051F300-GS [DX1016]
C8051F301-GM@QFN11 [DX4007]
C8051F302@QFN11 [DX4007]
C8051F302-GS [DX1016]
C8051F303-GM@QFN11 [DX4007]
C8051F304@QFN11 [DX4007]
C8051F304-GS [DX1016]
C8051F305-GM@QFN11 [DX4007]
C8051F310@TQFP32 [DX3001]
C8051F310A-GQ@TQFP32 [DX3001]
C8051F311@QFN28 [DX4013]
C8051F312@TQFP32 [DX3001]
C8051F313@QFN28 [DX4013]
C8051F314@TQFP32 [DX3001]
C8051F315@QFN28 [DX4013]
C8051F316-GM@QFN24 [DX4012]
C8051F320@TQFP32 [DX3001]
C8051F320A-GQ@TQFP32 [DX3001]
C8051F321@QFN28 [DX4013]
C8051F326-GM@QFN28 [DX4013]
C8051F327@QFN28 [DX4013]
C8051F327-GQ@QFN28 [DX4013]
C8051F330D [DX0001]
C8051F330-GP [DX0001]
C8051F331-GM@MLP20 [DX4011]
C8051F332-GM@MLP20 [DX4011]
C8051F333-GM@MLP20 [DX4011]
C8051F334-GM@MLP20 [DX4011]
C8051F335-GM@MLP20 [DX4011]
C8051F336-GM@MLP20 [DX4011]
C8051F337-GM@MLP20 [DX4011]
C8051F338-GM@MLP24 [DX4012]
C8051F339-GM@MLP24 [DX4012]

C8051F340@TQFP48 [DX3007]
C8051F341@TQFP48 [DX3007]
C8051F342@LQFP32 [DX3001]
C8051F343@LQFP32 [DX3001]
C8051F344@TQFP48 [DX3007]
C8051F345@TQFP48 [DX3007]
C8051F346@LQFP32 [DX3001]
C8051F347@LQFP32 [DX3001]
C8051F348@TQFP48 [DX3007]
C8051F349@LQFP32 [DX3001]
C8051F34A@LQFP32 [DX3001]
C8051F34B@LQFP32 [DX3001]
C8051F34C@TQFP48 [DX3007]
C8051F350-GQ@LQFP32 [DX3001]
C8051F352-GQ@LQFP32 [DX3001]
C8051F360@QFP48 [DX3007]
C8051F362@QFN28 [DX4013]
C8051F364@QFP32 [DX3001]
C8051F366@QFP32 [DX3001]
C8051F368@QFP32 [DX3001]
C8051F370-A-GM [DX4012]
C8051F371-A-GM [DX4012]
C8051F374-A-GM [DX4012]
C8051F375-A-GM [DX4012]
C8051F380@TQFP48 [DX3007]
C8051F381@TQFP32 [DX3001]
C8051F383@QFN32 [DX4015]
C8051F384@TQFP48 [DX3007]
C8051F385@TQFP32 [DX3001]
C8051F387@QFN32 [DX4015]
C8051F390-A-GM [DX4012]
C8051F391-A-GM [DX4012]
C8051F392-A-GM [DX4011]
C8051F393-A-GM [DX4011]
C8051F394-A-GM [DX4012]
C8051F395-A-GM [DX4012]
C8051F396-A-GM [DX4011]
C8051F397-A-GM [DX4011]
C8051F398-A-GM [DX4011]
C8051F399-A-GM [DX4011]
C8051F410@LQFP32 [DX3001]
C8051F411@QFN28 [DX4013]
C8051F412@LQFP32 [DX3001]
C8051F413@QFN28 [DX4013]
C8051F500-IM@QFN48 [DX4021]
C8051F501-IM@QFN48 [DX4021]
C8051F502-IM@QFN32 [DX4015]
C8051F503-IM@QFN32 [DX4015]
C8051F340-GQ@TQFP48 [DX3007]
C8051F341-GQ@TQFP48 [DX3007]
C8051F342-GQ@LQFP32 [DX3001]
C8051F343-GQ@LQFP32 [DX3001]
C8051F344-GQ@TQFP48 [DX3007]
C8051F345-GQ@TQFP48 [DX3007]
C8051F346-GQ@LQFP32 [DX3001]
C8051F347-GQ@LQFP32 [DX3001]
C8051F348-GQ@TQFP48 [DX3007]
C8051F349-GQ@LQFP32 [DX3001]
C8051F34A-GQ@LQFP32 [DX3001]
C8051F34B-GQ@LQFP32 [DX3001]
C8051F34D@LQFP32 [DX3001]
C8051F351-GM@QFN28 [DX4013]
C8051F353-GM@QFN28 [DX4013]
C8051F361@QFP32 [DX3001]
C8051F363@QFP48 [DX3007]
C8051F365@QFN28 [DX4013]
C8051F367@QFN28 [DX4013]
C8051F369@QFN28 [DX4013]
C8051F370-GM [DX4012]
C8051F371-GM [DX4012]
C8051F374-GM [DX4012]
C8051F375-GM [DX4012]
C8051F381@QFN32 [DX4015]
C8051F382@TQFP48 [DX3007]
C8051F383@TQFP32 [DX3001]
C8051F385@QFN32 [DX4015]
C8051F386@TQFP48 [DX3007]
C8051F387@TQFP32 [DX3001]
C8051F390-GM [DX4012]
C8051F391-GM [DX4012]
C8051F392-GM [DX4011]
C8051F393-GM [DX4011]
C8051F394-GM [DX4012]
C8051F395-GM [DX4012]
C8051F396-GM [DX4011]
C8051F397-GM [DX4011]
C8051F398-GM [DX4011]
C8051F399-GM [DX4011]
C8051F410-GQ@LQFP32 [DX3001]
C8051F411-GM@QFN28 [DX4013]
C8051F412-GQ@LQFP32 [DX3001]
C8051F413-GM@QFN28 [DX4013]
C8051F500-IQ@QFP48 [DX3007]
C8051F501-IQ@QFP48 [DX3007]
C8051F502-IQ@QFP32 [DX3001]
C8051F503-IQ@QFP32 [DX3001]

C8051F504-IM@QFN48 [DX4021]	C8051F504-IQ@QFP48 [DX3007]
C8051F505-IM@QFN48 [DX4021]	C8051F505-IQ@QFP48 [DX3007]
C8051F506-IM@QFN32 [DX4015]	C8051F506-IQ@QFP32 [DX3001]
C8051F507-IM@QFN32 [DX4015]	C8051F507-IQ@QFP32 [DX3001]
C8051F508-IM@QFN40 [DX4017]	C8051F509-IM@QFN40 [DX4017]
C8051F510-IM@QFN40 [DX4017]	C8051F511-IM@QFN40 [DX4017]
C8051F520A-IM@QFN10 [DX4007]	C8051F520-IM@QFN10 [DX4007]
C8051F521A-IM@QFN10 [DX4007]	C8051F521-IM@QFN10 [DX4007]
C8051F523A-IM@QFN10 [DX4007]	C8051F523-IM@QFN10 [DX4007]
C8051F524A-IM@QFN10 [DX4007]	C8051F524-IM@QFN10 [DX4007]
C8051F526A-IM@QFN10 [DX4007]	C8051F526-IM@QFN10 [DX4007]
C8051F527A-IM@QFN10 [DX4007]	C8051F527-IM@QFN10 [DX4007]
C8051F530A-IM@QFN20 [DX4011]	C8051F530A-IT@TSSOP20 [DX1000]
C8051F530-IM@QFN20 [DX4011]	C8051F530-IT@TSSOP20 [DX1000]
C8051F531A-IM@QFN20 [DX4011]	C8051F531A-IT@TSSOP20 [DX1000]
C8051F531-IM@QFN20 [DX4011]	C8051F531-IT@TSSOP20 [DX1000]
C8051F533A-IM@QFN20 [DX4011]	C8051F533A-IT@TSSOP20 [DX1000]
C8051F533-IM@QFN20 [DX4011]	C8051F533-IT@TSSOP20 [DX1000]
C8051F534A-IM@QFN20 [DX4011]	C8051F534A-IT@TSSOP20 [DX1000]
C8051F534-IM@QFN20 [DX4011]	C8051F534-IT@TSSOP20 [DX1000]
C8051F536A-IM@QFN20 [DX4011]	C8051F536A-IT@TSSOP20 [DX1000]
C8051F536-IM@QFN20 [DX4011]	C8051F536-IT@TSSOP20 [DX1000]
C8051F537A-IM@QFN20 [DX4011]	C8051F537A-IT@TSSOP20 [DX1000]
C8051F537-IM@QFN20 [DX4011]	C8051F537-IT@TSSOP20 [DX1000]
C8051F540-IM@QFN32 [DX4015]	C8051F540-IQ@QFP32 [DX3001]
C8051F541-IM@QFN32 [DX4015]	C8051F541-IQ@QFP32 [DX3001]
C8051F542-IM@QFN24 [DX4012]	C8051F543-IM@QFN24 [DX4012]
C8051F544-IM@QFN32 [DX4015]	C8051F544-IQ@QFP32 [DX3001]
C8051F545-IM@QFN32 [DX4015]	C8051F545-IQ@QFP32 [DX3001]
C8051F546-IM@QFN24 [DX4012]	C8051F547-IM@QFN24 [DX4012]
C8051F550-IM@QFN24 [DX4012]	C8051F551-IM@QFN24 [DX4012]
C8051F552-IM@QFN24 [DX4012]	C8051F553-IM@QFN24 [DX4012]
C8051F554-IM@QFN24 [DX4012]	C8051F555-IM@QFN24 [DX4012]
C8051F556-IM@QFN24 [DX4012]	C8051F557-IM@QFN24 [DX4012]
C8051F560-IM@QFN32 [DX4015]	C8051F560-IQ@QFP32 [DX3001]
C8051F561-IM@QFN32 [DX4015]	C8051F561-IQ@QFP32 [DX3001]
C8051F562-IM@QFN32 [DX4015]	C8051F562-IQ@QFP32 [DX3001]
C8051F563-IM@QFN32 [DX4015]	C8051F563-IQ@QFP32 [DX3001]
C8051F564-IM@QFN32 [DX4015]	C8051F564-IQ@QFP32 [DX3001]
C8051F565-IM@QFN32 [DX4015]	C8051F565-IQ@QFP32 [DX3001]
C8051F566-IM@QFN32 [DX4015]	C8051F566-IQ@QFP32 [DX3001]
C8051F567-IM@QFN32 [DX4015]	C8051F567-IQ@QFP32 [DX3001]
C8051F568-IM@QFN40 [DX4017]	C8051F569-IM@QFN40 [DX4017]
C8051F570-IM@QFN40 [DX4017]	C8051F571-IM@QFN40 [DX4017]
C8051F572-IM@QFN40 [DX4017]	C8051F573-IM@QFN40 [DX4017]
C8051F574-IM@QFN40 [DX4017]	C8051F575-IM@QFN40 [DX4017]
C8051F580-AM@QFN48 [DX4021]	C8051F580-AQ@QFP48 [DX3047]
C8051F580-IM@QFN48 [DX4021]	C8051F580-IQ@QFP48 [DX3047]

C8051F581-AM@QFN48 [DX4021]
C8051F581-IM@QFN48 [DX4021]
C8051F582-AM@QFN32 [DX4015]
C8051F582-IM@QFN32 [DX4015]
C8051F583-AM@QFN32 [DX4015]
C8051F583-IM@QFN32 [DX4015]
C8051F584-AM@QFN48 [DX4021]
C8051F584-IM@QFN48 [DX4021]
C8051F585-AM@QFN48 [DX4021]
C8051F585-IM@QFN48 [DX4021]
C8051F586-AM@QFN32 [DX4015]
C8051F586-IM@QFN32 [DX4015]
C8051F587-AM@QFN32 [DX4015]
C8051F587-IM@QFN32 [DX4015]
C8051F588-AM@QFN40 [DX4017]
C8051F589-AM@QFN40 [DX4017]
C8051F590-AM@QFN40 [DX4017]
C8051F591-AM@QFN40 [DX4017]
C8051F700-GQ@QFP64 [DX3011]
C8051F702-GQ@QFP64 [DX3011]
C8051F704-GM@QFN48 [DX4021]
C8051F705-GM@QFN48 [DX4021]
C8051F706-GM@QFN48 [DX4021]
C8051F707-GM@QFN48 [DX4021]
C8051F708-GQ@QFP64 [DX3011]
C8051F710-GQ@QFP64 [DX3011]
C8051F712-GM@QFN48 [DX4021]
C8051F713-GM@QFN48 [DX4021]
C8051F714-GM@QFN48 [DX4021]
C8051F715-GM@QFN48 [DX4021]
C8051F716-GM [DX4015]
C8051F750B-GM [DX4021]
C8051F750-GM [DX4021]
C8051F751B-GM [DX4015]
C8051F752B-GM [DX4012]
C8051F755B-GM [DX4021]
C8051F755-GM [DX4021]
C8051F756B-GM [DX4015]
C8051F757B-GM [DX4012]
C8051F760-GM [DX4021]
C8051F761-GM [DX4015]
C8051F765-GM [DX4021]
C8051F766-GM [DX4015]
C8051F800-GM@QFN20 [DX4011]
C8051F801-GM@QFN20 [DX4011]
C8051F802-GM@QFN20 [DX4011]
C8051F803-GS@SOIC16 [DX1016]
C8051F805-GS@SOIC16 [DX1016]
C8051F581-AQ@QFP48 [DX3047]
C8051F581-IQ@QFP48 [DX3047]
C8051F582-AQ@QFP32 [DX3001]
C8051F582-IQ@QFP32 [DX3001]
C8051F583-AQ@QFP32 [DX3001]
C8051F583-IQ@QFP32 [DX3001]
C8051F584-AQ@QFP48 [DX3047]
C8051F584-IQ@QFP48 [DX3047]
C8051F585-AQ@QFP48 [DX3047]
C8051F585-IQ@QFP48 [DX3047]
C8051F586-AQ@QFP32 [DX3001]
C8051F586-IQ@QFP32 [DX3001]
C8051F587-AQ@QFP32 [DX3001]
C8051F587-IQ@QFP32 [DX3001]
C8051F588-IM@QFN40 [DX4017]
C8051F589-IM@QFN40 [DX4017]
C8051F590-IM@QFN40 [DX4017]
C8051F591-IM@QFN40 [DX4017]
C8051F701-GQ@QFP64 [DX3011]
C8051F703-GQ@QFP64 [DX3011]
C8051F704-GQ@QFP48 [DX3047]
C8051F705-GQ@QFP48 [DX3047]
C8051F706-GQ@QFP48 [DX3047]
C8051F707-GQ@QFP48 [DX3047]
C8051F709-GQ@QFP64 [DX3011]
C8051F711-GQ@QFP64 [DX3011]
C8051F712-GQ@QFP48 [DX3047]
C8051F713-GQ@QFP48 [DX3047]
C8051F714-GQ@QFP48 [DX3047]
C8051F715-GQ@QFP48 [DX3047]
C8051F717-GM [DX4012]
C8051F750B-GM1 [DX4043]
C8051F750-GM1 [DX4043]
C8051F751-GM [DX4015]
C8051F752-GM [DX4012]
C8051F755B-GM1 [DX4043]
C8051F755-GM1 [DX4043]
C8051F756-GM [DX4015]
C8051F757-GM [DX4012]
C8051F760-GM1 [DX4043]
C8051F762-GM [DX4012]
C8051F765-GM1 [DX4043]
C8051F767-GM [DX4012]
C8051F800-GU@QSOP24 [DX1001]
C8051F801-GU@QSOP24 [DX1001]
C8051F802-GU@QSOP24 [DX1001]
C8051F804-GS@SOIC16 [DX1016]
C8051F806-GM@QFN20 [DX4011]

C8051F806-GU@QSOP24 [DX1001]
C8051F807-GU@QSOP24 [DX1001]
C8051F808-GU@QSOP24 [DX1001]
C8051F810-GS@SOIC16 [DX1016]
C8051F812-GM@QFN20 [DX4011]
C8051F813-GM@QFN20 [DX4011]
C8051F814-GM@QFN20 [DX4011]
C8051F815-GS@SOIC16 [DX1016]
C8051F817-GS@SOIC16 [DX1016]
C8051F818-GU@QSOP24 [DX1001]
C8051F819-GU@QSOP24 [DX1001]
C8051F820-GU@QSOP24 [DX1001]
C8051F822-GS@SOIC16 [DX1016]
C8051F824-GS@SOIC16 [DX1016]
C8051F826-GS@SOIC16 [DX1016]
C8051F828-GS@SOIC16 [DX1016]
C8051F830-GS@SOIC16 [DX1016]
C8051F832-GS@SOIC16 [DX1016]
C8051F834-GS@SOIC16 [DX1016]
C8051F850-C-GM [DX4038]
C8051F851-C-GM [DX4038]
C8051F852-C-GM [DX4038]
C8051F853-C-GM [DX4038]
C8051F854-C-GM [DX4038]
C8051F855-C-GM [DX4038]
C8051F860-C-GS [DX1016]
C8051F862-C-GS [DX1016]
C8051F864-C-GS [DX1016]
C8051F901-GM@QFN24 [DX4012]
C8051F902-GM@QFN24 [DX4012]
C8051F911-GM@QFN24 [DX4012]
C8051F912-GM@QFN24 [DX4012]
C8051F920-F-GM@QFN32 [DX4015]
C8051F920-GM@QFN32 [DX4015]
C8051F921-F-GM@QFN24 [DX4012]
C8051F930-F-GM@QFN32 [DX4015]
C8051F930-GM@QFN32 [DX4015]
C8051F931-F-GM@QFN24 [DX4012]
C8051F960A-GM [DX0001]
C8051F960-GM [DX0001]
C8051F961A-GM [DX4017]
C8051F962A-GM [DX0001]
C8051F962-GM [DX0001]
C8051F963A-GM [DX4017]
C8051F964A-GM [DX0001]
C8051F964-GM [DX0001]
C8051F965A-GM [DX4017]
C8051F966A-GM [DX0001]
C8051F807-GM@QFN20 [DX4011]
C8051F808-GM@QFN20 [DX4011]
C8051F809-GS@SOIC16 [DX1016]
C8051F811-GS@SOIC16 [DX1016]
C8051F812-GU@QSOP24 [DX1001]
C8051F813-GU@QSOP24 [DX1001]
C8051F814-GU@QSOP24 [DX1001]
C8051F816-GS@SOIC16 [DX1016]
C8051F818-GM@QFN20 [DX4011]
C8051F819-GM@QFN20 [DX4011]
C8051F820-GM@QFN20 [DX4011]
C8051F821-GS@SOIC16 [DX1016]
C8051F823-GS@SOIC16 [DX1016]
C8051F825-GS@SOIC16 [DX1016]
C8051F827-GS@SOIC16 [DX1016]
C8051F829-GS@SOIC16 [DX1016]
C8051F831-GS@SOIC16 [DX1016]
C8051F833-GS@SOIC16 [DX1016]
C8051F835-GS@SOIC16 [DX1016]
C8051F850-C-GU [DX1001]
C8051F851-C-GU [DX1001]
C8051F852-C-GU [DX1001]
C8051F853-C-GU [DX1001]
C8051F854-C-GU [DX1001]
C8051F855-C-GU [DX1001]
C8051F861-C-GS [DX1016]
C8051F863-C-GS [DX1016]
C8051F865-C-GS [DX1016]
C8051F901-GU@QSOP24 [DX1001]
C8051F902-GU@QSOP24 [DX1001]
C8051F911-GU@QSOP24 [DX1001]
C8051F912-GU@QSOP24 [DX1001]
C8051F920-F-GQ@LQFP32 [DX3001]
C8051F920-GQ@LQFP32 [DX3001]
C8051F921-GM@QFN24 [DX4012]
C8051F930-F-GQ@LQFP32 [DX3001]
C8051F930-GQ@LQFP32 [DX3001]
C8051F931-GM@QFN24 [DX4012]
C8051F960A-GQ [DX3016]
C8051F960-GQ [DX3016]
C8051F961-GM [DX4017]
C8051F962A-GQ [DX3016]
C8051F962-GQ [DX3016]
C8051F963-GM [DX4017]
C8051F964A-GQ [DX3016]
C8051F964-GQ [DX3016]
C8051F965-GM [DX4017]
C8051F966A-GQ [DX3016]

C8051F966-GM [DX0001]
C8051F966-GQ [DX3016]
C8051F967A-GM [DX4017]
C8051F967-GM [DX4017]
C8051F968A-GM [DX0001]
C8051F968A-GQ [DX3016]
C8051F968-GM [DX0001]
C8051F968-GQ [DX3016]
C8051F969A-GM [DX4017]
C8051F969-GM [DX4017]
C8051F980-GM [DX4038]
C8051F981-GM [DX4038]
C8051F982-GM [DX4038]
C8051F983-GM [DX4038]
C8051F985-GM [DX4038]
C8051F986-GM [DX4012]
C8051F986-GU [DX1001]
C8051F987-GM [DX4012]
C8051F987-GU [DX1001]
C8051F988-GM [DX4012]
C8051F988-GU [DX1001]
C8051F989-GM [DX4012]
C8051F989-GU [DX1001]
C8051F990-GM [DX4038]
C8051F991-GM [DX4038]
C8051F996-GM [DX4012]
C8051F996-GU [DX1001]
C8051F997-GM [DX4012]
C8051F997-GU [DX1001]
C8051T320-GQ@LQFP32 [DX3001]
C8051T321-GM@QFN28 [DX4013]
C8051T322-GQ@LQFP32 [DX3001]
C8051T323-GM@QFN28 [DX4013]
C8051T326-GM@QFN28 [DX4013]
C8051T327-GM@QFN28 [DX4013]
C8051T600@QFN11 [DX4007]
C8051T600@TSSOP14 [DX1016]
C8051T601@QFN11 [DX4007]
C8051T601@TSSOP14 [DX1016]
C8051T602@QFN11 [DX4007]
C8051T602@TSSOP14 [DX1016]
C8051T603@QFN11 [DX4007]
C8051T603@TSSOP14 [DX1016]
C8051T604@QFN11 [DX4007]
C8051T604@TSSOP14 [DX1016]
C8051T605@QFN11 [DX4007]
C8051T605@TSSOP14 [DX1016]
C8051T606@MSOP10 [DX1051]
C8051T606@QFN10 [DX4035]
C8051T606@QFN11 [DX4007]
C8051T610-GQ@LQFP32 [DX3001]
C8051T610-GQ@LQFP32(old) [DX3001]
C8051T611-GM@QFN28 [DX4013]
C8051T611-GM@QFN28(old) [DX4013]
C8051T612-GQ@LQFP32 [DX3001]
C8051T612-GQ@LQFP32(old) [DX3001]
C8051T613-GM@QFN28 [DX4013]
C8051T613-GM@QFN28(old) [DX4013]
C8051T614-GQ@LQFP32 [DX3001]
C8051T614-GQ@LQFP32(old) [DX3001]
C8051T615-GM@QFN28 [DX4013]
C8051T615-GM@QFN28(old) [DX4013]
C8051T616-GM@QFN24 [DX4012]
C8051T616-GM@QFN24(old) [DX4012]
C8051T617-GM@QFN24 [DX4012]
C8051T617-GM@QFN24(old) [DX4012]
C8051T620-GM@QFN32 [DX4015]
C8051T621-GM@QFN32 [DX4015]
C8051T622-GM@QFN24 [DX4012]
C8051T623-GM@QFN24 [DX4012]
C8051T626-B-GM [DX4015]
C8051T627-B-GM [DX4015]
C8051T630@QFN20 [DX4011]
C8051T631@QFN20 [DX4011]
C8051T632@QFN20 [DX4011]
C8051T633@QFN20 [DX4011]
C8051T634@QFN20 [DX4011]
C8051T635@QFN20 [DX4011]
SI1000@QFN42(ISP) [DX0001]
SI1001@QFN42(ISP) [DX0001]
SI1002@QFN42(ISP) [DX0001]
SI1003@QFN42(ISP) [DX0001]
SI1004@QFN42(ISP) [DX0001]
SI1005@QFN42(ISP) [DX0001]
SI1010@QFN42(ISP) [DX0001]
SI1011@QFN42(ISP) [DX0001]
SI1012@QFN42(ISP) [DX0001]
SI1013@QFN42(ISP) [DX0001]
SI1014@QFN42(ISP) [DX0001]
SI1015@QFN42(ISP) [DX0001]

SI1020_A_GM(ISP) [DX0001]
SI1021_A_GM(ISP) [DX0001]
SI1022_A_GM(ISP) [DX0001]
SI1023_A_GM(ISP) [DX0001]
SI1024_A_GM(ISP) [DX0001]
SI1025_A_GM(ISP) [DX0001]
SI1026_A_GM(ISP) [DX0001]
SI1027_A_GM(ISP) [DX0001]
SI1030_A_GM(ISP) [DX0001]
SI1031_A_GM(ISP) [DX0001]
SI1032_A_GM(ISP) [DX0001]
SI1033_A_GM(ISP) [DX0001]
SI1034_A_GM(ISP) [DX0001]
SI1035_A_GM(ISP) [DX0001]
SI1036_A_GM(ISP) [DX0001]
SI1037_A_GM(ISP) [DX0001]
SI1060_A_GM(ISP) [DX0001]
SI1061_A_GM(ISP) [DX0001]
SI1062_A_GM(ISP) [DX0001]
SI1063_A_GM(ISP) [DX0001]
SI1064_A_GM(ISP) [DX0001]
SI1065_A_GM(ISP) [DX0001]
SI1080_A_GM(ISP) [DX0001]
SI1081_A_GM(ISP) [DX0001]
SI1082_A_GM(ISP) [DX0001]
SI1083_A_GM(ISP) [DX0001]
SI1084_A_GM(ISP) [DX0001]
SI1085_A_GM(ISP) [DX0001]
SI4010-C2-AS [DX1016]
SI4010-C2-AT [DX1051]
SI4010-C2-GS [DX1016]
SI4010-C2-GT [DX1051]
SI8250@LQFP32 [DX3001]
SI8250@QFN28 [DX4013]
SI8250-IM@QFN28 [DX4013]
SI8250-IQ@LQFP32 [DX3001]
SI8251@LQFP32 [DX3001]
SI8251@QFN28 [DX4013]
SI8251-IM@QFN28 [DX4013]
SI8251-IQ@LQFP32 [DX3001]
SI8252@LQFP32 [DX3001]
SI8252@QFN28 [DX4013]
SI8252-IM@QFN28 [DX4013]
SI8252-IQ@LQFP32 [DX3001]

SILICON7

E(E)PROM/FRAM/NVRAM

SV4E1602UBA@FBGA56 [DX5045]
SV4E1602UTA@FBGA56 [DX5045]
SV4E1604UBA@FBGA56 [DX5045]
SV4E1604UTA@FBGA56 [DX5045]
SV4E1608UBA@FBGA56 [DX5045]
SV4E1608UTA@FBGA56 [DX5045]
SV4E3204UBA@FBGA56 [DX5045]
SV4E3204UTA@FBGA56 [DX5045]
SV4E3208UBA@FBGA56 [DX5001]
SV4E3208UTA@FBGA56 [DX5045]
SV4E3216UBA@FBGA56 [DX5045]
SV4E3216UTA@FBGA56 [DX5045]
SV4F1602UBA@FBGA66 [DX5005]
SV4F1602UTA@FBGA66 [DX5005]
SV4F1604UBA@FBGA66 [DX5005]
SV4F1604UTA@FBGA66 [DX5005]
SV4F1608UBA@FBGA66 [DX5005]
SV4F1608UTA@FBGA66 [DX5005]
SV4F3204UBA@FBGA66 [DX5005]
SV4F3204UTA@FBGA66 [DX5005]
SV4F3208UBA@FBGA66 [DX5005]
SV4F3208UTA@FBGA66 [DX5005]
SV4F3216UBA@FBGA66 [DX5005]
SV4F3216UTA@FBGA66 [DX5005]
SV5C2832UCR@FBGA72 [DX5001]
SV5C3238UBA(NO EFP)@FBGA72 [DX5001]
SV5C3238UBA@FBGA72 [DX5001]
SV5C3238UTA(NO EFP)@FBGA72 [DX5001]
SV5C3238UTA@FBGA72 [DX5001]
SV5C6408UBR(NO EFP)@FBGA72 [DX5001]
SV5C6408UBR@FBGA72 [DX5001]
SV5C6408UTR(NO EFP)@FBGA72 [DX5001]

SV5C6408UTR@FBGA72 [DX5001]
SV5C6416UBB(NO EFP)@FBGA72 [DX5001]
SV5C6416UBB@FBGA72 [DX5001]
SV5C6416UBR(NO EFP)@FBGA72 [DX5001]
SV5C6416UBR@FBGA72 [DX5001]
SV5C6416UTB(NO EFP)@FBGA72 [DX5001]
SV5C6416UTB@FBGA72 [DX5001]
SV5C6416UTR(NO EFP)@FBGA72 [DX5001]
SV5C6416UTR@FBGA72 [DX5001]
SV5C6432UBR(NO EFP)@FBGA72 [DX5001]
SV5C6432UBR@FBGA72 [DX5001]
SV5C6432UTR(NO EFP)@FBGA72 [DX5001]

SV5C6432UTR@FBGA72 [DX5001]	SV5D2832UCA@FBGA88 [DX5005]
SV6C2832UBA@FBGA72 [DX5001]	SV6C2832UTA@FBGA72 [DX5001]
SV6C2864UBA@FBGA72 [DX5001]	SV6C2864UTA@FBGA72 [DX5001]
SV6C6416UBA@FBGA72 [DX5001]	SV6C6416UTA@FBGA72 [DX5001]
SV6C6432UBA@FBGA72 [DX5001]	SV6C6432UTA@FBGA72 [DX5001]
SV6D2832UBA@FBGA88 [DX5001]	SV6D2832UTA@FBGA88 [DX5001]
SV7C1602UBA@FBGA72 [DX5001]	SV7C1602UTA@FBGA72 [DX5001]
SV7C1604UBA@FBGA72 [DX5001]	SV7C1604UTA@FBGA72 [DX5001]
SV7C1608UBA@FBGA72 [DX5001]	SV7C1608UTA@FBGA72 [DX5001]
SV7C3204UBA@FBGA72 [DX5001]	SV7C3204UTA@FBGA72 [DX5001]
SV7C3208UBA@FBGA72 [DX5001]	SV7C3208UTA@FBGA72 [DX5001]
SV7C3216UBA@FBGA72 [DX5001]	SV7C3216UTA@FBGA72 [DX5001]
SV7E1602UBA@FBGA56 [DX5001]	SV7E1602UBAL@FBGA56 [DX5045]
SV7E1602UTA@FBGA56 [DX5001]	SV7E1602UTAL@FBGA56 [DX5045]
SV7E1604UBA@FBGA56 [DX5001]	SV7E1604UBAL@FBGA56 [DX5045]
SV7E1604UTA@FBGA56 [DX5001]	SV7E1604UTAL@FBGA56 [DX5045]
SV7E1608UBA@FBGA56 [DX5001]	SV7E1608UBALC@FBGA56 [DX5045]
SV7E1608UTA@FBGA56 [DX5001]	SV7E1608UTALC@FBGA56 [DX5045]
SV7E3204UBA@FBGA56 [DX5001]	SV7E3204UBAL@FBGA56 [DX5045]
SV7E3204UTA@FBGA56 [DX5001]	SV7E3204UTAL@FBGA56 [DX5045]
SV7E3208UBA@FBGA56 [DX5001]	SV7E3208UBALC@FBGA56 [DX5045]
SV7E3208UTA@FBGA56 [DX5001]	SV7E3208UTALC@FBGA56 [DX5045]
SV7E3216UBA@FBGA56 [DX5001]	SV7E3216UBALC@FBGA56 [DX5045]
SV7E3216UTA@FBGA56 [DX5001]	SV7E3216UTALC@FBGA56 [DX5045]
SVME2832UBA@FBGA56 [DX5045]	SVME2832UTA@FBGA56 [DX5045]
SVME2864UBA@FBGA56 [DX5045]	SVME2864UTA@FBGA56 [DX5045]
SVME3204UBA@FBGA56 [DX5045]	SVME3204UTA@FBGA56 [DX5045]
SVME3208UBA@FBGA56 [DX5045]	SVME3208UTA@FBGA56 [DX5045]
SVME3216UBA@FBGA56 [DX5045]	SVME3216UTA@FBGA56 [DX5045]
SVME6416UBA@FBGA56 [DX5045]	SVME6416UTA@FBGA56 [DX5045]
SVME6432UBA@FBGA56 [DX5045]	SVME6432UTA@FBGA56 [DX5045]

SIMTEK

E(E)PROM/FRAM/NVRAM

STK10C48 [DX0001]
STK10C48@SOIC28(300 mil) [DX1033]
STK10C48@SOIC28(350 mil) [DX1035]
STK10C68 [DX0001]
STK10C68@PLCC28 [DX2028]
STK10C68@SOIC28 [DX1035]
STK11C48 [DX0001]
STK11C48@SOIC28(300 mil) [DX1033]
STK11C48@SOIC28(350 mil) [DX1035]
STK11C68 [DX0001]
STK11C68@PLCC28 [DX2028]
STK11C68@SOIC28 [DX1035]
STK11C88 [DX0001]
STK11C88(3V) [DX0001]
STK11C88(3V)@SOIC28(300 mil) [DX1033]
STK11C88(3V)@SOIC28(350 mil) [DX1035]
STK11C88@SOIC28(300 mil) [DX1033]
STK11C88@SOIC28(350 mil) [DX1035]
STK12C68 [DX0001]
STK12C68@PLCC28 [DX2028]
STK12C68@SOIC28 [DX1035]
STK14C88 [DX0001]
STK14C88(3V) [DX0001]
STK14C88(3V)@PLCC32 [DX2032]
STK14C88(3V)@SOIC32(300 mil) [DX1036]
STK14C88(3V)@SOIC32(350 mil) [DX1035]
STK14C88@PLCC32 [DX2032]
STK14C88@SOIC32(300 mil) [DX1036]
STK14C88@SOIC32(350 mil) [DX1035]
STK15C68 [DX0001]
STK15C68@SOIC28 [DX1035]
STK15C88 [DX0001]
STK15C88@SOIC28(300 mil) [DX1033]
STK15C88@SOIC28(350 mil) [DX1035]
STK16C68 [DX0001]
STK16C88 [DX0001]
STK16C88(3V) [DX0001]
STK20C04 [DX0001]
STK22C48 [DX0001]
STK22C48@SOIC28(300 mil) [DX1033]
STK22C48@SOIC28(350 mil) [DX1035]
STK25C48 [DX0001]

SINOWEALTH

MICROCONTROLLER

SH66P51A@LQFP44 [DX3002]
SH66P51A@LQFP64 [DX3057]
SH67P33 [DX0001]
SH67P33@SOIC20 [DX1033]
SH67P33@SSOP20 [DX1067]
SH67P33C [DX0001]
SH67P33C@SOIC20 [DX1033]
SH67P33C@SSOP20 [DX1067]
SH77P1651@LQFP48 [DX3007]
SH79F081AM [DX1036]
SH79F083@SOIC20 [DX1033]
SH79F085@SSOP20 [DX1001]
SH79F161A [DX3001]
SH79F161A@QFP32 [DX3001]
SH79F161A@QFP44 [DX3002]
SH79F165@SOP24 [DX1033]
SH79F165@SOP28 [DX1033]
SH79F166@QFP44 [DX3002]

SH79F166A@QFP44 [DX3002]
SH79F166F@QFP44 [DX3002]
SH79F169B@QFP48 [DX3007]
SH79F321@QFP44 [DX3002]
SH79F321F@QFP44 [DX3002]
SH79F3283@QFP44 [DX3005]
SH79F3283@QFP48 [DX3007]
SH79F3284@QFP44 [DX3005]
SH79F3284@QFP48 [DX3007]
SH79F6421@QFP64 [DX3085]
SH79F6421S@QFP64 [DX3085]
SH79F642B@QFP64 [DX3011]
SH79F642BP@QFP64 [DX3085]
SH79F6484@QFP44 [DX3005]
SH79F6484@QFP48 [DX3007]
SH79F7010@QFP64 [DX3085]
SH79F7010P@QFP100 [DX3021]
SH79F7012@QFP64 [DX3085]
SH79F7012P@QFP80 [DX3016]
SH79F7016@QFP64 [DX3085]
SH79M081AM@SOIC28 [DX1036]
SH86F313@QFP48 [DX3007]

SIRF

E(E)PROM/FRAM/NVRAM

GSC3F(LP)-7979@FBGA140 [DX5065]
GSC3F(LPx)-7879@FBGA140 [DX5065]
GSC3F-7879@FBGA140 [DX5065]
GSC3F-7979@FBGA140 [DX5065]
GSC3F-7989@FBGA140 [DX5065]
GSC3F-7990@FBGA140 [DX5065]

SMI

MICROCONTROLLER

SM3712@QFN40 [DX4039-1]
SM3732@QFN40 [DX4039-2]

SMOS

E(E)PROM/FRAM/NVRAM

SPM27128 [DX0001]
SPM27128C [DX0001]
SPM27C256 [DX0001]
SPM27C64 [DX0001]
SPM27C64H [DX0001]

SMSC

E(E)PROM/FRAM/NVRAM

MEC1619L@BGA156 [DX5204]

SONIX

MICROCONTROLLER

SN8P1504 [DX0001]
SN8P1504@SOP18 [DX1033]
SN8P1504@SOP28 [DX1033]
SN8P1506 [DX0001]
SN8P1507@TQFP44 [DX3002]
SN8P1602 [DX0001]
SN8P1602@SOP18 [DX1033]
SN8P1602@SSOP20 [DX1025]
SN8P1603 [DX0001]
SN8P1603@SOP18 [DX1033]
SN8P1603@SSOP20 [DX1025]
SN8P1604 [DX0001]
SN8P1604@SOP28 [DX1033]
SN8P1702 [DX0001]
SN8P1702@SOP18 [DX1033]
SN8P1702@SSOP20 [DX1025]
SN8P1704A [DX0001]
SN8P1704A@SOP28 [DX1033]
SN8P1704B [DX0001]
SN8P1704B@SOP28 [DX1033]
SN8P1706A [DX0001]
SN8P1706B [DX0001]
SN8P1707A [DX0001]
SN8P1707A@TQFP44 [DX3002]
SN8P1707B@TQFP44 [DX3002]
SN8P1708A [DX0001]
SN8P1708A@SSOP48 [DX1028]
SN8P1708B [DX0001]
SN8P1708B@SSOP48 [DX1028]
SN8P1714 [DX0001]
SN8P1714@SOP18 [DX1033]
SN8P1714@SOP28 [DX1033]
SN8P1716 [DX0001]
SN8P1717@TQFP44 [DX3002]
SN8P2501AP [DX0001]
SN8P2501AS@SOP14 [DX1016]
SN8P2501AX@TSSOP16 [DX1000]
SN8P2501BP [DX0001]
SN8P2501BS@SOP14 [DX1016]
SN8P2501BX@TSSOP16 [DX1000]
SN8P2502AP [DX0001]
SN8P2502AS@SOP14 [DX1016]
SN8P2502AX@TSSOP16 [DX1000]
SN8P2502BP [DX0001]
SN8P2502BS@SOP14 [DX1016]
SN8P2502BX@TSSOP16 [DX1000]
SN8P2504AP [DX0001]
SN8P2504AS@SOP14 [DX1016]
SN8P2504AX@TSSOP16 [DX1000]
SN8P2504BP [DX0001]
SN8P2504BS@SOP14 [DX1016]
SN8P2504BX@TSSOP16 [DX1000]
SN8P2602AP [DX0001]
SN8P2602AS@SOP18 [DX1031]
SN8P2602AX@SSOP20 [DX1025]
SN8P2602BP [DX0001]
SN8P2602BS@SOP18 [DX1031]
SN8P2602BX@SSOP20 [DX1025]
SN8P2603AP [DX0001]
SN8P2603AS@SOP18 [DX1031]
SN8P2603AX@SSOP20 [DX1025]
SN8P2603BP [DX0001]
SN8P2603BS@SOP18 [DX1031]
SN8P2603BX@SSOP20 [DX1025]
SN8P26042AP [DX0001]
SN8P26042AS@SOP20 [DX1031]
SN8P26042AX@SSOP20 [DX1025]
SN8P26042BP [DX0001]
SN8P26042BS@SOP20 [DX1031]
SN8P26042BX@SSOP20 [DX1025]
SN8P26042P [DX0001]
SN8P26042S@SOP20 [DX1031]
SN8P26042X@SSOP20 [DX1025]
SN8P2604AK [DX0001]
SN8P2604AS@SOP28 [DX1033]
SN8P2604AX@SSOP28 [DX1026]
SN8P2604BK [DX0001]
SN8P2604BS@SOP28 [DX1033]
SN8P2604BX@SSOP28 [DX1026]
SN8P2604K [DX0001]
SN8P2604S@SOP28 [DX1033]
SN8P2604X@SSOP28 [DX1026]
SN8P2606P [DX0001]
SN8P2608P [DX0001]
SN8P2608X@SSOP48 [DX1028]
SN8P2622P [DX0001]
SN8P2622S@SOP18 [DX1031]
SN8P2622X@SSOP20 [DX1024]
SN8P2624K [DX0001]
SN8P2624S@SOP28 [DX1033]
SN8P2624X@SSOP28 [DX1026]
SN8P2704AK@SDIP28 [DX0032]
SN8P2704AP [DX0001]
SN8P2704AS@SOP28 [DX1018]
SN8P2705AP [DX0001]
SN8P2705AS@SOP32 [DX1020]

SN8P2706AP [DX0001]
SN8P2707AQ@QFP44 [DX3002]
SN8P2708AP [DX0001]
SN8P2708AQ@LQFP48 [DX3007]
SN8P2708AX@SSOP48 [DX1028]
SN8P2722P [DX0001]
SN8P2722S@SOP20 [DX1031]
SN8P2722X@SSOP20 [DX1024]

SONY

E(E)PROM/FRAM/NVRAM

CXK1011M@SOIC8 [DX1045]
CXK1011P [DX0001]
CXK1012P [DX0001]
CXK1013P [DX0001]
CXK1023P [DX0001]
CXK27C4001 [DX0001]

DRAM & SRAM

CXK581000 [DX0001]
CXK581000@SOIC32 [DX1035]

SPACE ELECTRONICS[SEi]

E(E)PROM/FRAM/NVRAM

28C010 [DX0001]
28C010@PLCC32 [DX2032]
28C010@TSOP32 [DX1002]
28C010T [DX0001]
28C010T@PLCC32 [DX2032]
28C010T@TSOP32 [DX1002]
28C011 [DX0001]
28C011@PLCC32 [DX2032]
28C011@TSOP32 [DX1002]
28C011T [DX0001]
28C011T@PLCC32 [DX2032]
28C011T@TSOP32 [DX1002]

SPANSION

E(E)PROM/FRAM/NVRAM

AM29BDD160GB@FBGA80 [DX5258]
AM29BDD160GB@PQFP80 [DX3020]
AM29BDD160GT@FBGA80 [DX5258]
AM29BDD160GT@PQFP80 [DX3020]
AM29BL162CB@SSOP56 [DX1029]
AM29BL802CB@SSOP56 [DX1029]
AM29DL161DB@FBGA48 [DX5022]
AM29DL161DB@FBGA63 [DX5047]
AM29DL161DB@FBGA64 [DX5074]
AM29DL161DB@TSOP48 [DX1004]
AM29DL161DB@VFBGA48 [DX5043]
AM29DL161DT@FBGA48 [DX5022]
AM29DL161DT@FBGA63 [DX5047]
AM29DL161DT@FBGA64 [DX5074]
AM29DL161DT@TSOP48 [DX1004]
AM29DL161DT@VFBGA48 [DX5043]
AM29DL162CB@FBGA48 [DX5022]
AM29DL162CB@TSOP48 [DX1004]
AM29DL162CT@FBGA48 [DX5022]
AM29DL162CT@TSOP48 [DX1004]
AM29DL162DB@FBGA48 [DX5022]
AM29DL162DB@FBGA63 [DX5047]
AM29DL162DB@FBGA64 [DX5074]
AM29DL162DB@TSOP48 [DX1004]
AM29DL162DB@VFBGA48 [DX5043]
AM29DL162DT@FBGA48 [DX5022]

AM29DL162DT@FBGA63 [DX5047]
AM29DL162DT@FBGA64 [DX5074]
AM29DL162DT@TSOP48 [DX1004]
AM29DL162DT@VFBGA48 [DX5043]
AM29DL163CB@FBGA48 [DX5022]
AM29DL163CB@TSOP48 [DX1004]
AM29DL163CT@FBGA48 [DX5022]
AM29DL163CT@TSOP48 [DX1004]
AM29DL163DB@FBGA48 [DX5022]
AM29DL163DB@FBGA63 [DX5047]
AM29DL163DB@FBGA64 [DX5074]
AM29DL163DB@TSOP48 [DX1004]
AM29DL163DB@VFBGA48 [DX5043]
AM29DL163DT@FBGA48 [DX5022]
AM29DL163DT@FBGA63 [DX5047]
AM29DL163DT@FBGA64 [DX5074]
AM29DL163DT@TSOP48 [DX1004]
AM29DL163DT@VFBGA48 [DX5043]
AM29DL164CB@FBGA48 [DX5022]
AM29DL164CB@TSOP48 [DX1004]
AM29DL164CT@FBGA48 [DX5022]
AM29DL164CT@TSOP48 [DX1004]
AM29DL164DB@FBGA48 [DX5022]
AM29DL164DB@FBGA63 [DX5047]
AM29DL164DB@FBGA64 [DX5074]
AM29DL164DB@TSOP48 [DX1004]
AM29DL164DB@VFBGA48 [DX5043]
AM29DL164DT@FBGA48 [DX5022]
AM29DL164DT@FBGA63 [DX5047]
AM29DL164DT@FBGA64 [DX5074]
AM29DL164DT@TSOP48 [DX1004]
AM29DL164DT@VFBGA48 [DX5043]
AM29DL320GB@FBGA48 [DX5063]
AM29DL320GB@FBGA63 [DX5051]
AM29DL320GB@FBGA64 [DX5074]
AM29DL320GB@TSOP48 [DX1004]
AM29DL320GT@FBGA48 [DX5063]
AM29DL320GT@FBGA63 [DX5051]
AM29DL320GT@FBGA64 [DX5074]
AM29DL320GT@TSOP48 [DX1004]
AM29DL321CB@TSOP48 [DX1004]
AM29DL321CT@TSOP48 [DX1004]
AM29DL322CB@FBGA63 [DX5051]
AM29DL322CB@TSOP48 [DX1004]
AM29DL322CT@FBGA63 [DX5051]
AM29DL322CT@TSOP48 [DX1004]
AM29DL322DB@FBGA63 [DX5051]
AM29DL322DB@TSOP48 [DX1004]
AM29DL322DT@FBGA63 [DX5051]
AM29DL322DT@TSOP48 [DX1004]
AM29DL322GB@FBGA48 [DX5063]
AM29DL322GB@FBGA63 [DX5051]
AM29DL322GB@FBGA64 [DX5074]
AM29DL322GB@TSOP48 [DX1004]
AM29DL322GT@FBGA48 [DX5063]
AM29DL322GT@FBGA63 [DX5051]
AM29DL322GT@FBGA64 [DX5074]
AM29DL322GT@TSOP48 [DX1004]
AM29DL323CB@FBGA63 [DX5051]
AM29DL323CB@TSOP48 [DX1004]
AM29DL323CT@FBGA63 [DX5051]
AM29DL323CT@TSOP48 [DX1004]
AM29DL323DB@FBGA48 [DX5022]
AM29DL323DB@FBGA63 [DX5051]
AM29DL323DB@TSOP48 [DX1004]
AM29DL323DT@FBGA48 [DX5022]
AM29DL323DT@FBGA63 [DX5051]
AM29DL323DT@TSOP48 [DX1004]
AM29DL323GB@FBGA48 [DX5063]
AM29DL323GB@FBGA63 [DX5051]
AM29DL323GB@FBGA64 [DX5074]
AM29DL323GB@TSOP48 [DX1004]
AM29DL323GT@FBGA48 [DX5063]
AM29DL323GT@FBGA63 [DX5051]
AM29DL323GT@FBGA64 [DX5074]
AM29DL323GT@TSOP48 [DX1004]
AM29DL324CB@TSOP48 [DX1004]
AM29DL324CT@TSOP48 [DX1004]
AM29DL324DB@FBGA63 [DX5051]
AM29DL324DB@TSOP48 [DX1004]
AM29DL324DT@FBGA63 [DX5051]
AM29DL324DT@TSOP48 [DX1004]
AM29DL324GB@FBGA48 [DX5063]
AM29DL324GB@FBGA63 [DX5051]
AM29DL324GB@FBGA64 [DX5074]
AM29DL324GB@TSOP48 [DX1004]
AM29DL324GT@FBGA48 [DX5063]
AM29DL324GT@FBGA63 [DX5051]
AM29DL324GT@FBGA64 [DX5074]
AM29DL324GT@TSOP48 [DX1004]
AM29DL400BB(REVERSE)@TSOP48 [DX1004]
AM29DL400BB@PSOP44 [DX1014]
AM29DL400BB@TSOP48 [DX1004]
AM29DL400BT(REVERSE)@TSOP48 [DX1004]

AM29DL400BT@PLCC44 [DX1014]
AM29DL400BT@TSOP48 [DX1004]
AM29DL640D@FBGA63 [DX5041]
AM29DL640D@TSOP48 [DX1004]
AM29DL640G@FBGA63 [DX5041]
AM29DL640G@FBGA64 [DX5074]
AM29DL640G@TSOP48 [DX1004]
AM29DL642G@FBGA63 [DX5041]
AM29DL800B@PSOP44 [DX1014]
AM29DL800B@TSOP48 [DX1004]
AM29DL800BB(REVERSE)@TSOP48 [DX1004]
AM29DL800BB@FBGA48 [DX5039]
AM29DL800BB@PSOP44 [DX1014]
AM29DL800BB@TSOP48 [DX1004]
AM29DL800BT(REVERSE)@TSOP48 [DX1004]
AM29DL800BT@FBGA48 [DX5039]
AM29DL800BT@PSOP44 [DX1014]
AM29DL800BT@TSOP48 [DX1004]
AM29DL800T@PSOP44 [DX1014]
AM29DL800T@TSOP48 [DX1004]
AM29DS163CB@TSOP48 [DX1004]
AM29DS163CT@TSOP48 [DX1004]
AM29DS163DB@FBGA48 [DX5002]
AM29DS163DB@TSOP48 [DX1004]
AM29DS163DT@FBGA48 [DX5002]
AM29DS163DT@TSOP48 [DX1004]
AM29DS323DB@FBGA48 [DX5002]
AM29DS323DB@TSOP48 [DX1004]
AM29DS323DT@FBGA48 [DX5002]
AM29DS323DT@TSOP48 [DX1004]
AM29F002B [DX0001]
AM29F002B@PLCC32 [DX2032]
AM29F002B@TSOP32 [DX1002]
AM29F002BB [DX0001]
AM29F002BB@PLCC32 [DX2032]
AM29F002BB@TSOP32 [DX1002]
AM29F002BT [DX0001]
AM29F002BT@PLCC32 [DX2032]
AM29F002BT@TSOP32 [DX1002]
AM29F002NB [DX0001]
AM29F002NB@PLCC32 [DX2032]
AM29F002NB@TSOP32 [DX1002]
AM29F002NBB [DX0001]
AM29F002NBB@PLCC32 [DX2032]
AM29F002NBB@TSOP32 [DX1002]
AM29F002NBT [DX0001]
AM29F002NBT@PLCC32 [DX2032]
AM29F002NBT@TSOP32 [DX1002]
AM29F002NT [DX0001]
AM29F002NT@PLCC32 [DX2032]
AM29F002NT@TSOP32 [DX1002]
AM29F002T [DX0001]
AM29F002T@PLCC32 [DX2032]
AM29F002T@TSOP32 [DX1002]
AM29F004BB [DX0001]
AM29F004BB@PLCC32 [DX2032]
AM29F004BB@TSOP32 [DX1002]
AM29F004BT [DX0001]
AM29F004BT@PLCC32 [DX2032]
AM29F004BT@TSOP32 [DX1002]
AM29F016@PSOP44 [DX1014]
AM29F016@TSOP40 [DX1006]
AM29F016@TSOP48 [DX1004]
AM29F016B@PSOP44 [DX1014]
AM29F016B@TSOP40 [DX1006]
AM29F016B@TSOP48 [DX1004]
AM29F016D@PSOP44 [DX1014]
AM29F016D@TSOP40 [DX1006]
AM29F016D@TSOP48 [DX1004]
AM29F017B(REVERSE)@TSOP40 [DX1006]
AM29F017B(REVERSE)@TSOP48 [DX1004]
AM29F017B@TSOP40 [DX1006]
AM29F017B@TSOP48 [DX1004]
AM29F017D(REVERSE)@TSOP48 [DX1004]
AM29F017D@TSOP40 [DX1006]
AM29F017D@TSOP48 [DX1004]
AM29F032B@PSOP44 [DX1014]
AM29F032B@TSOP40 [DX1006]
AM29F040 [DX0001]
AM29F040@PLCC32 [DX2032]
AM29F040@TSOP32 [DX1002]
AM29F040A [DX0001]
AM29F040A@PLCC32 [DX2032]
AM29F040A@TSOP32 [DX1002]
AM29F040B [DX0001]
AM29F040B(Reverse)@TSOP32 [DX1002]
AM29F040B@PLCC32 [DX2032]
AM29F040B@TSOP32 [DX1002]

AM29F080(REVERSE)@TSOP40 [DX1006]
AM29F080@PSOP44 [DX1014]
AM29F080@TSOP40 [DX1006]
AM29F080B@PSOP44 [DX1014]
AM29F080B@TSOP40 [DX1006]
AM29F100B(REVERSE)@TSOP48 [DX1004]
AM29F100B@PSOP44 [DX1014]
AM29F100B@TSOP48 [DX1004]
AM29F100T(REVERSE)@TSOP48 [DX1004]
AM29F100T@PSOP44 [DX1014]
AM29F100T@TSOP48 [DX1004]
AM29F160DB(REVERSE)@TSOP48 [DX1004]
AM29F160DB@TSOP48 [DX1004]
AM29F160DT(REVERSE)@TSOP48 [DX1004]
AM29F160DT@TSOP48 [DX1004]
AM29F200AB(REVERSE)@TSOP48 [DX1004]
AM29F200AB@PSOP44 [DX1014]
AM29F200AB@TSOP48 [DX1004]
AM29F200AT(REVERSE)@TSOP48 [DX1004]
AM29F200AT@PSOP44 [DX1014]
AM29F200AT@TSOP48 [DX1004]
AM29F200BB(REVERSE)@TSOP48 [DX1004]
AM29F200BB@PSOP44 [DX1014]
AM29F200BB@TSOP48 [DX1004]
AM29F200BT(REVERSE)@TSOP48 [DX1004]
AM29F200BT@PSOP44 [DX1014]
AM29F200BT@TSOP48 [DX1004]
AM29F400AB(REVERSE)@TSOP48 [DX1004]
AM29F400AB@PSOP44 [DX1014]
AM29F400AB@TSOP48 [DX1004]
AM29F400AT(REVERSE)@TSOP48 [DX1004]
AM29F400AT@PSOP44 [DX1014]
AM29F400AT@TSOP48 [DX1004]
AM29F400BB(REVERSE)@TSOP48 [DX1004]
AM29F400BB@PSOP44 [DX1014]
AM29F400BB@TSOP48 [DX1004]
AM29F400BT(REVERSE)@TSOP48 [DX1004]
AM29F400BT@PSOP44 [DX1014]
AM29F400BT@TSOP48 [DX1004]
AM29F800B(REVERSE)@TSOP48 [DX1004]
AM29F800B@PSOP44 [DX1014]
AM29F800B@TSOP48 [DX1004]
AM29F800BB(REVERSE)@TSOP48 [DX1004]
AM29F800BB@FBGA48 [DX5039]
AM29F800BB@PSOP44 [DX1014]
AM29F800BB@TSOP48 [DX1004]
AM29F800BT(REVERSE)@TSOP48 [DX1004]
AM29F800BT@FBGA48 [DX5039]
AM29F800BT@PSOP44 [DX1014]
AM29F800BT@TSOP48 [DX1004]
AM29F800T(REVERSE)@TSOP48 [DX1004]
AM29F800T@PSOP44 [DX1014]
AM29F800T@TSOP48 [DX1004]
AM29LL800B@TSOP48 [DX1004]
AM29LL800BB@TSOP48 [DX1004]
AM29LL800BT@TSOP48 [DX1004]
AM29LL800T@TSOP48 [DX1004]
AM29LV001BB(REVERSE)@TSOP32 [DX1002]
AM29LV001BB@PLCC32 [DX2032]
AM29LV001BB@TSOP32 [DX1002]
AM29LV001BT(REVERSE)@TSOP32 [DX1002]
AM29LV001BT@PLCC32 [DX2032]
AM29LV001BT@TSOP32 [DX1002]
AM29LV002@TSOP40 [DX1006]
AM29LV002B@TSOP40 [DX1006]
AM29LV002BB@TSOP40 [DX1006]
AM29LV002BT@TSOP40 [DX1006]
AM29LV004B@TSOP40 [DX1006]
AM29LV004BB@TSOP40 [DX1006]
AM29LV004BT@TSOP40 [DX1006]
AM29LV004T@TSOP40 [DX1006]
AM29LV008B@TSOP40 [DX1006]
AM29LV008BB@TSOP40 [DX1006]

AM29LV008BT@TSOP40 [DX1006]　　AM29LV008T@TSOP40 [DX1006]
AM29LV017B(REVERSE)@TSOP40 [DX1006]
AM29LV017B@FBGA48 [DX5022]　　AM29LV017B@TSOP40 [DX1006]
AM29LV017D(REVERSE)@TSOP40 [DX1006]
AM29LV017D@FBGA48 [DX5022]　　AM29LV017D@TSOP40 [DX1006]
AM29LV033C@FBGA63 [DX5051]　　AM29LV033C@TSOP40 [DX1006]
AM29LV033MU@FBGA48 [DX5022]　　AM29LV033MU@TSOP40 [DX1006]
AM29LV065D@FBGA63 [DX5041]　　AM29LV065D@TSOP48 [DX1004]
AM29LV065MU@FBGA63 [DX5041]　　AM29LV065MU@TSOP48 [DX1004]
AM29LV080@TSOP40 [DX1006]　　AM29LV081@TSOP40 [DX1006]
AM29LV081B@TSOP40 [DX1006]　　AM29LV116BB@TSOP40 [DX1006]
AM29LV116BT@TSOP40 [DX1006]　　AM29LV116DB@TSOP40 [DX1006]
AM29LV116DT@TSOP40 [DX1006]
AM29LV128MH(REVERSE)@TSOP56 [DX1011]
AM29LV128MH@FBGA64 [DX5074]　　AM29LV128MH@TSOP56 [DX1011]
AM29LV128ML(REVERSE)@TSOP56 [DX1011]
AM29LV128ML@FBGA64 [DX5074]　　AM29LV128ML@TSOP56 [DX1011]
AM29LV160BB(REVERSE)@TSOP48 [DX1004]
AM29LV160BB@FBGA48 [DX5022]　　AM29LV160BB@PSOP44 [DX1014]
AM29LV160BB@TSOP48 [DX1004]
AM29LV160BT(REVERSE)@TSOP48 [DX1004]
AM29LV160BT@FBGA48 [DX5022]　　AM29LV160BT@PSOP44 [DX1014]
AM29LV160BT@TSOP48 [DX1004]
AM29LV160DB(REVERSE)@TSOP48 [DX1004]
AM29LV160DB@FBGA48 [DX5022]　　AM29LV160DB@PSOP44 [DX1014]
AM29LV160DB@TSOP48 [DX1004]
AM29LV160DT(REVERSE)@TSOP48 [DX1004]
AM29LV160DT@FBGA48 [DX5022]　　AM29LV160DT@PSOP44 [DX1014]
AM29LV160DT@TSOP48 [DX1004]　　AM29LV160MA@PSOP44 [DX1014]
AM29LV160MB(REVERSE)@TSOP48 [DX1004]
AM29LV160MB@FBGA48 [DX5022]　　AM29LV160MB@FBGA64 [DX5074]
AM29LV160MB@PSOP44 [DX1014]　　AM29LV160MB@TSOP48 [DX1004]
AM29LV160MT(REVERSE)@TSOP48 [DX1004]
AM29LV160MT@FBGA48 [DX5022]　　AM29LV160MT@FBGA64 [DX5074]
AM29LV160MT@PSOP44 [DX1014]　　AM29LV160MT@TSOP48 [DX1004]
AM29LV200B(REVERSE)@TSOP48 [DX1004]
AM29LV200B@PSOP44 [DX1014]　　AM29LV200B@TSOP48 [DX1004]
AM29LV200BB(REVERSE)@TSOP48 [DX1004]
AM29LV200BB@FBGA48 [DX5002]　　AM29LV200BB@PSOP44 [DX1014]
AM29LV200BB@TSOP48 [DX1004]
AM29LV200BT(REVERSE)@TSOP48 [DX1004]
AM29LV200BT@FBGA48 [DX5002]　　AM29LV200BT@PSOP44 [DX1014]
AM29LV200BT@TSOP48 [DX1004]
AM29LV200T(REVERSE)@TSOP48 [DX1004]
AM29LV200T@PSOP44 [DX1014]　　AM29LV200T@TSOP48 [DX1004]
AM29LV256MH(REVERSE)@TSOP56 [DX1011]
AM29LV256MH@FBGA64 [DX5075]　　AM29LV256MH@TSOP56 [DX1011]
AM29LV256ML(REVERSE)@TSOP56 [DX1011]

AM29LV256ML@FBGA64 [DX5075]
AM29LV256ML@TSOP56 [DX1011]
AM29LV320DB@FBGA48 [DX5040]
AM29LV320DB@TSOP48 [DX1004]
AM29LV320DT@FBGA48 [DX5040]
AM29LV320DT@TSOP48 [DX1004]
AM29LV320FB@TSOP48 [DX1004]
AM29LV320FT@TSOP48 [DX1004]
AM29LV320MB@FBGA48 [DX5022]
AM29LV320MB@FBGA64 [DX5074]
AM29LV320MB@TSOP48 [DX1004]
AM29LV320MH(REVERSE)@TSOP56 [DX1011]
AM29LV320MH@FBGA64 [DX5074]
AM29LV320MH@TSOP56 [DX1011]
AM29LV320ML(REVERSE)@TSOP56 [DX1011]
AM29LV320ML@FBGA64 [DX5074]
AM29LV320ML@TSOP56 [DX1011]
AM29LV320MT@FBGA48 [DX5022]
AM29LV320MT@FBGA64 [DX5074]
AM29LV320MT@TSOP48 [DX1004]
AM29LV400B(REVERSE)@TSOP48 [DX1004]
AM29LV400B@FBGA48 [DX5002]
AM29LV400B@PSOP44 [DX1014]
AM29LV400B@TSOP48 [DX1004]
AM29LV400BB(REVERSE)@TSOP48 [DX1004]
AM29LV400BB@FBGA48 [DX5002]
AM29LV400BB@PSOP44 [DX1014]
AM29LV400BB@TSOP48 [DX1004]
AM29LV400BT(REVERSE)@TSOP48 [DX1004]
AM29LV400BT@FBGA48 [DX5002]
AM29LV400BT@PSOP44 [DX1014]
AM29LV400BT@TSOP48 [DX1004]
AM29LV400T(REVERSE)@TSOP48 [DX1004]
AM29LV400T@FBGA48 [DX5002]
AM29LV400T@PSOP44 [DX1014]
AM29LV400T@TSOP48 [DX1004]
AM29LV640DH@SSOP56 [DX1029]
AM29LV640DL@SSOP56 [DX1029]
AM29LV640DU@FBGA63 [DX5041]
AM29LV640DU@FBGA64 [DX5074]
AM29LV640GU@FBGA63 [DX5041]
AM29LV640GU@FBGA64 [DX5074]
AM29LV640MB@FBGA63 [DX5041]
AM29LV640MB@FBGA64 [DX5074]
AM29LV640MB@TSOP48 [DX1004]
AM29LV640MH(REVERSE)@TSOP56 [DX1011]
AM29LV640MH@FBGA64 [DX5074]
AM29LV640MH@TSOP56 [DX1011]
AM29LV640ML(REVERSE)@TSOP56 [DX1011]
AM29LV640ML@FBGA64 [DX5074]
AM29LV640ML@TSOP56 [DX1011]
AM29LV640MT@FBGA63 [DX5041]
AM29LV640MT@FBGA64 [DX5074]
AM29LV640MT@TSOP48 [DX1004]
AM29LV640MU@FBGA63 [DX5041]
AM29LV640MU@FBGA64 [DX5074]
AM29LV641DH(REVERSE)@TSOP48 [DX1004]
AM29LV641DH@TSOP48 [DX1004]
AM29LV641DL(REVERSE)@TSOP48 [DX1004]
AM29LV641DL@TSOP48 [DX1004]
AM29LV641GH(REVERSE)@TSOP48 [DX1004]
AM29LV641GH@TSOP48 [DX1004]
AM29LV641GL(REVERSE)@TSOP48 [DX1004]
AM29LV641GL@TSOP48 [DX1004]
AM29LV641MH(REVERSE)@TSOP48 [DX1004]
AM29LV641MH@TSOP48 [DX1004]
AM29LV641ML(REVERSE)@TSOP48 [DX1004]
AM29LV641ML@TSOP48 [DX1004]
AM29LV642D@FBGA64 [DX5074]
AM29LV642G@FBGA64 [DX5074]
AM29LV652D@FBGA63 [DX5041]

AM29LV800B(REVERSE)@TSOP48 [DX1004]
AM29LV800B@PSOP44 [DX1014]
AM29LV800B@TSOP48 [DX1004]
AM29LV800BB(REVERSE)@TSOP48 [DX1004]
AM29LV800BB@FBGA48 [DX5039]
AM29LV800BB@PSOP44 [DX1014]
AM29LV800BB@TSOP48 [DX1004]
AM29LV800BT(REVERSE)@TSOP48 [DX1004]
AM29LV800BT@FBGA48 [DX5039]
AM29LV800BT@PSOP44 [DX1014]
AM29LV800BT@TSOP48 [DX1004]
AM29LV800DB(REVERSE)@TSOP48 [DX1004]
AM29LV800DB(WB)@FBGA48 [DX5039]
AM29LV800DB(WC)@FBGA48 [DX5043]
AM29LV800DB@PSOP44 [DX1014]
AM29LV800DB@TSOP48 [DX1004]
AM29LV800DT(REVERSE)@TSOP48 [DX1004]
AM29LV800DT(WB)@FBGA48 [DX5039]
AM29LV800DT(WC)@FBGA48 [DX5043]
AM29LV800DT@PSOP44 [DX1014]
AM29LV800DT@TSOP48 [DX1004]
AM29LV800T(REVERSE)@TSOP48 [DX1004]
AM29LV800T@PSOP44 [DX1014]
AM29LV800T@TSOP48 [DX1004]
AM29PDL128G70(REVERSE)@FBGA80 [DX5147]
AM29PDL128G70@FBGA80 [DX5147]
AM29PDL128G80@FBGA80 [DX5147]
AM29PDL128G90@FBGA80 [DX5147]
AM29PDS322DB@FBGA48 [DX50UN]
AM29PDS322DT@FBGA48 [DX50UN]
AM29PL160BB@PSOP44 [DX1014]
AM29PL160BB@TSOP48 [DX1004]
AM29PL160CB@PSOP44 [DX1014]
AM29PL160CB@TSOP48 [DX1004]
AM29PL160CT@PSOP44 [DX1014]
AM29PL160CT@TSOP48 [DX1004]
AM29SL160BB@FBGA48 [DX5022]
AM29SL160BB@TSOP48 [DX1004]
AM29SL160BT@FBGA48 [DX5022]
AM29SL160BT@TSOP48 [DX1004]
AM29SL160CB@FBGA48 [DX5022]
AM29SL160CB@TSOP48 [DX1004]
AM29SL160CT@FBGA48 [DX5022]
AM29SL160CT@TSOP48 [DX1004]
AM29SL400CB@FBGA48 [DX5002]
AM29SL400CB@TSOP48 [DX1004]
AM29SL400CT@FBGA48 [DX5002]
AM29SL400CT@TSOP48 [DX1004]
AM29SL800BB(REVERSE)@TSOP48 [DX1004]
AM29SL800BB@FBGA48 [DX5039]
AM29SL800BB@TSOP48 [DX1004]
AM29SL800BT(REVERSE)@TSOP48 [DX1004]
AM29SL800BT@FBGA48 [DX5039]
AM29SL800BT@TSOP48 [DX1004]
AM29SL800CB(REVERSE)@TSOP48 [DX1004]
AM29SL800CB@FBGA48 [DX5039]
AM29SL800CB@TSOP48 [DX1004]
AM29SL800CT(REVERSE)@TSOP48 [DX1004]
AM29SL800CT@FBGA48 [DX5039]
AM29SL800CT@TSOP48 [DX1004]
AM29SL800DB(REVERSE)@TSOP48 [DX1004]
AM29SL800DB@TSOP48 [DX1004]
AM29SL800DBUF@FBGA48 [DX5038]
AM29SL800DBVG@FBGA48 [DX5038]
AM29SL800DBVU@FBGA48 [DX5043]
AM29SL800DBWA@FBGA48 [DX5002]
AM29SL800DBWC@FBGA48 [DX5022]
AM29SL800DT(REVERSE)@TSOP48 [DX1004]
AM29SL800DT@TSOP48 [DX1004]
AM29SL800DTUF@FBGA48 [DX5038]
AM29SL800DTVG@FBGA48 [DX5038]
AM29SL800DTVU@FBGA48 [DX5043]
AM29SL800DTWA@FBGA48 [DX5002]
AM29SL800DTWC@FBGA48 [DX5022]
AT29BDS640GB73@FBGA64 [DX50UN]
AT29BDS640GB74@FBGA64 [DX50UN]
AT29BDS640GB78@FBGA64 [DX50UN]
AT29BDS640GB79@FBGA64 [DX50UN]
AT29BDS640GB93@FBGA64 [DX50UN]
AT29BDS640GB94@FBGA64 [DX50UN]

AT29BDS640GB98@FBGA64 [DX50UN]　　AT29BDS640GB99@FBGA64 [DX50UN]
AT29BDS640GT73@FBGA64 [DX50UN]　　AT29BDS640GT74@FBGA64 [DX50UN]
AT29BDS640GT78@FBGA64 [DX50UN]　　AT29BDS640GT79@FBGA64 [DX50UN]
AT29BDS640GT93@FBGA64 [DX50UN]　　AT29BDS640GT94@FBGA64 [DX50UN]
AT29BDS640GT98@FBGA64 [DX50UN]　　AT29BDS640GT99@FBGA64 [DX50UN]
BS128HD5V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD6V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD8V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HD9V(AM29BDS128HD)@FBGA80 [DX5053]
BS128HE5V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE6V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE8V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HE9V(AM29BDS128HE)@FBGA80 [DX5053]
BS128HF5V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF6V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF8V(AM29BDS128HF)@FBGA80 [DX5053]
BS128HF9V(AM29BDS128HF)@FBGA80 [DX5053]
BS640HD8V(AM29BDS640HD)@FBGA64 [DX5053]
BS640HD9V(AM29BDS640HD)@FBGA64 [DX5053]
BS640HE8V(AM29BDS640HE)@FBGA64 [DX5053]
BS640HE9V(AM29BDS640HE)@FBGA64 [DX5053]
BS640HF8V(AM29BDS640HF)@FBGA64 [DX5053]
BS640HF9V(AM29BDS640HF)@FBGA64 [DX5053]
DS42514(AM29DL1634DB)@FBGA69 [DX5001]
DS42515(AM29DL1644DB)@FBGA69 [DX5001]
DS42516(AM29DL324DB)@FBGA73 [DX5001]
DS42546(AM29DL1634DT)@FBGA69 [DX5001]
DS42553(AM29DL323DT)@FBGA73 [DX5001]
DS42585(AM29DL323DT)@FBGA73 [DX5001]
DS42587(AM29DL324DB)@FBGA73 [DX5001]
DS42629(AM29DL640G)@VFBGA48 [DX5080]
DS42677(AM29LV128MH/L)@FBGA88 [DX5053]
DS42678(AM29LV320MT)@FBGA67 [DX5001]
DS42689(AM29LV320MT)@FBGA64 [DX5004]
DS42690(AM29LV320MB)@FBGA64 [DX5004]
DS42695(AM29LV320MT)@FBGA64 [DX5074]
DS42696(AM29LV320MB)@FBGA64 [DX5074]
DS42701(AM29LV640MU)@FBGA88 [DX5053]
DS42725(AM50DL128CH)@FBGA88 [DX5001]
DS42772A(AM29LV640M)@FBGA88 [DX5053]
M410000000(AM41DL1614DT)@FBGA69 [DX5001]
M410000001(AM41DL1614DB)@FBGA69 [DX5001]
M410000002(AM41DL1614DT)@FBGA69 [DX5001]
M410000003(AM41DL1614DB)@FBGA69 [DX5001]
M410000004(AM41DL1624DT)@FBGA69 [DX5001]
M410000005(AM41DL1624DB)@FBGA69 [DX5001]
M410000006(AM41DL1624DT)@FBGA69 [DX5001]
M410000007(AM41DL1624DB)@FBGA69 [DX5001]

M410000008(AM41DL1634DT)@FBGA69 [DX5001]
M410000009(AM41DL1634DB)@FBGA69 [DX5001]
M41000000A(AM41DL1634DT)@FBGA69 [DX5001]
M41000000B(AM41DL1634DB)@FBGA69 [DX5001]
M41000000C(AM41DL1644DT)@FBGA69 [DX5001]
M41000000D(AM41DL1644DB)@FBGA69 [DX5001]
M41000000E(AM41DL1644DT)@FBGA69 [DX5001]
M41000000F(AM41DL1644DB)@FBGA69 [DX5001]
M41000000G(AM41DL6408G)@FBGA73 [DX5001]
M41000000H(AM41DL6408G)@FBGA73 [DX5001]
M41000001W(AM41DL3224GT)@FBGA73 [DX5001]
M41000001X(AM41DL3224GB)@FBGA73 [DX5001]
M41000001Y(AM41DL3224GT)@FBGA73 [DX5001]
M41000001Z(AM41DL3224GB)@FBGA73 [DX5001]
M410000020(AM41DL3234GT)@FBGA73 [DX5001]
M410000021(AM41DL3234GB)@FBGA73 [DX5001]
M410000022(AM41DL3234GT)@FBGA73 [DX5001]
M410000023(AM41DL3234GB)@FBGA73 [DX5001]
M410000024(AM41DL3244GT)@FBGA73 [DX5001]
M410000025(AM41DL3244GB)@FBGA73 [DX5001]
M410000026(AM41DL3244GT)@FBGA73 [DX5001]
M410000027(AM41DL3244GB)@FBGA73 [DX5001]
M41000002L(AM41DL3228GT)@FBGA73 [DX5001]
M41000002M(AM41DL3228GB)@FBGA73 [DX5001]
M41000002N(AM41DL3228GT)@FBGA73 [DX5001]
M41000002O(AM41DL3228GB)@FBGA73 [DX5001]
M41000002P(AM41DL3238GT)@FBGA73 [DX5001]
M41000002Q(AM41DL3238GB)@FBGA73 [DX5001]
M41000002R(AM41DL3238GT)@FBGA73 [DX5001]
M41000002S(AM41DL3238GB)@FBGA73 [DX5001]
M41000002T(AM41DL3248GT)@FBGA73 [DX5001]
M41000002U(AM41DL3248GB)@FBGA73 [DX5001]
M41000002V(AM41DL3248GT)@FBGA73 [DX5001]
M41000002W(AM41DL3248GB)@FBGA73 [DX5001]
M41000003D(AM41DL3208GT)@FBGA73 [DX5001]
M41000003E(AM41DL3208GB)@FBGA73 [DX5001]
M41000003F(AM41DL3208GT)@FBGA73 [DX5001]
M41000003G(AM41DL3208GB)@FBGA73 [DX5001]
M410000095(AM41LV3204MT)@FBGA69 [DX5005]
M410000096(AM41LV3204MB)@FBGA69 [DX5005]
M41000009B(AM41DL6408H)@FBGA73 [DX5001]
M41000009C(AM41DL6408H)@FBGA73 [DX5001]
M41000009D(AM41DL6408H)@FBGA73 [DX5001]
M420000000(AM42DL640AG)@FBGA73 [DX5001]
M420000001(AM42DL640AG)@FBGA73 [DX5001]
M420000004(AM42DL1642DT)@FBGA69 [DX5001]
M420000005(AM42DL1642DB)@FBGA69 [DX5001]
M420000006(AM42DL1642DT)@FBGA69 [DX5001]

M420000007(AM42DL1642DB)@FBGA69 [DX5001]
M42000000I(AM42DL1612DT)@FBGA69 [DX5001]
M42000000J(AM42DL1612DB)@FBGA69 [DX5001]
M42000000K(AM42DL1612DT)@FBGA69 [DX5001]
M42000000L(AM42DL1612DB)@FBGA69 [DX5001]
M42000000M(AM42DL1622DT)@FBGA69 [DX5001]
M42000000N(AM42DL1622DB)@FBGA69 [DX5001]
M420000000(AM42DL1622DT)@FBGA69 [DX5001]
M42000000P(AM42DL1622DB)@FBGA69 [DX5001]
M42000000Q(AM42DL1632DT)@FBGA69 [DX5001]
M42000000R(AM42DL1632DB)@FBGA69 [DX5001]
M42000000S(AM42DL1632DT)@FBGA69 [DX5001]
M42000000T(AM42DL1632DB)@FBGA69 [DX5001]
M42000000U(AM42DL1642DT)@FBGA69 [DX5001]
M42000000V(AM42DL1642DB)@FBGA69 [DX5001]
M42000000W(AM42DL1642DT)@FBGA69 [DX5001]
M42000000X(AM42DL1642DB)@FBGA69 [DX5001]
M42000001A(AM42DL1614DT)@FBGA69 [DX5001]
M42000001B(AM42DL1614DB)@FBGA69 [DX5001]
M42000001C(AM42DL1614DT)@FBGA69 [DX5001]
M42000001D(AM42DL1614DB)@FBGA69 [DX5001]
M42000001E(AM42DL1624DT)@FBGA69 [DX5001]
M42000001F(AM42DL1624DB)@FBGA69 [DX5001]
M42000001G(AM42DL1624DT)@FBGA69 [DX5001]
M42000001H(AM42DL1624DB)@FBGA69 [DX5001]
M42000001I(AM42DL1634DT)@FBGA69 [DX5001]
M42000001J(AM42DL1634DB)@FBGA69 [DX5001]
M42000001K(AM42DL1634DT)@FBGA69 [DX5001]
M42000001L(AM42DL1634DB)@FBGA69 [DX5001]
M42000001M(AM42DL1644DT)@FBGA69 [DX5001]
M42000001N(AM42DL1644DB)@FBGA69 [DX5001]
M42000001O(AM42DL1644DT)@FBGA69 [DX5001]
M42000001P(AM42DL1644DB)@FBGA69 [DX5001]
M420000022(AM42DL3224GT)@FBGA73 [DX5001]
M420000023(AM42DL3224GB)@FBGA73 [DX5001]
M420000024(AM42DL3224GT)@FBGA73 [DX5001]
M420000025(AM42DL3224GB)@FBGA73 [DX5001]
M420000026(AM42DL3234GT)@FBGA73 [DX5001]
M420000027(AM42DL3234GB)@FBGA73 [DX5001]
M420000028(AM42DL3234GT)@FBGA73 [DX5001]
M420000029(AM42DL3234GB)@FBGA73 [DX5001]
M42000002A(AM42DL3244GT)@FBGA73 [DX5001]
M42000002B(AM42DL3244GB)@FBGA73 [DX5001]
M42000002C(AM42DL3244GT)@FBGA73 [DX5001]
M42000002D(AM42DL3244GB)@FBGA73 [DX5001]
M42000002U(AM42DL6404G)@FBGA73 [DX5001]
M42000002V(AM42DL6404G)@FBGA73 [DX5001]
M42000002Y(AM42BDS6408GT)@FBGA93 [DX5001]

M420000002Z(AM42BDS6408GB)@FBGA93 [DX5001]
M420000030(AM42BDS6408GT)@FBGA93 [DX5001]
M420000031(AM42BDS6408GB)@FBGA93 [DX5001]
M420000032(AM42BDS6408GT)@FBGA93 [DX5001]
M420000033(AM42BDS6408GB)@FBGA93 [DX5001]
M420000034(AM42BDS6408GT)@FBGA93 [DX5001]
M420000035(AM42BDS6408GB)@FBGA93 [DX5001]
M42000004Y(AM42BDS640AGT)@FBGA93 [DX5001]
M42000004Z(AM42BDS640AGB)@FBGA93 [DX5001]
M420000050(AM42BDS640AGT)@FBGA93 [DX5001]
M420000051(AM42BDS640AGB)@FBGA93 [DX5001]
M420000052(AM42BDS640AGT)@FBGA93 [DX5001]
M420000053(AM42BDS640AGB)@FBGA93 [DX5001]
M420000054(AM42BDS640AGT)@FBGA93 [DX5001]
M420000055(AM42BDS640AGB)@FBGA93 [DX5001]
M42000005M(AM42DL6402G)@FBGA73 [DX5001]
M42000005N(AM42DL6402G)@FBGA73 [DX5001]
M42000005W(AM42DL3224GT)@FBGA73 [DX5001]
M42000005X(AM42DL3224GB)@FBGA73 [DX5001]
M42000005Y(AM42DL3234GT)@FBGA73 [DX5001]
M42000005Z(AM42DL3234GB)@FBGA73 [DX5001]
M420000060(AM42DL3244GT)@FBGA73 [DX5001]
M420000061(AM42DL3244GB)@FBGA73 [DX5001]
M420000070(AM42BDS6408HE8)@BGA89 [DX5005]
M420000071(AM42BDS6408HE9)@BGA89 [DX5005]
M420000072(AM42BDS6408HD8)@BGA89 [DX5005]
M420000073(AM42BDS6408HD9)@BGA89 [DX5005]
M420000074(AM42BDS6408HE3)@BGA89 [DX5005]
M420000075(AM42BDS6408HE4)@BGA89 [DX5005]
M420000076(AM42BDS6408HD3)@BGA89 [DX5005]
M420000077(AM42BDS6408HD4)@BGA89 [DX5005]
M420000078(AM42DL640AH)@FBGA73 [DX5001]
M420000079(AM42DL640AH)@FBGA73 [DX5001]
M450000000(AM45DL6408G)@FBGA73 [DX5001]
M450000001(AM45DL6408G)@FBGA73 [DX5001]
M450000008(AM45DL3208GT)@FBGA73 [DX5001]
M450000009(AM45DL3208GB)@FBGA73 [DX5001]
M45000000A(AM45DL3208GT)@FBGA73 [DX5001]
M45000000B(AM45DL3208GB)@FBGA73 [DX5001]
M45000000S(AM45DL3228GT)@FBGA73 [DX5001]
M45000000T(AM45DL3228GB)@FBGA73 [DX5001]
M45000000U(AM45DL3228GT)@FBGA73 [DX5001]
M45000000V(AM45DL3228GB)@FBGA73 [DX5001]
M45000001C(AM45DL3238GT)@FBGA73 [DX5001]
M45000001D(AM45DL3238GB)@FBGA73 [DX5001]
M45000001E(AM45DL3238GT)@FBGA73 [DX5001]
M45000001F(AM45DL3238GB)@FBGA73 [DX5001]
M45000001W(AM45DL3248GT)@FBGA73 [DX5001]

M45000001X(AM45DL3248GB)@FBGA73 [DX5001]
M45000001Y(AM45DL3248GT)@FBGA73 [DX5001]
M45000001Z(AM45DL3248GB)@FBGA73 [DX5001]
M490000000(AM49DL640BG)@FBGA73 [DX5001]
M490000001(AM49DL640BG)@FBGA73 [DX5001]
M49000000G(AM49DL320BGT)@FBGA73 [DX5001]
M49000000H(AM49DL320BGT)@FBGA73 [DX5001]
M49000000J(AM49DL322BGT)@FBGA73 [DX5001]
M49000000K(AM49DL322BGT)@FBGA73 [DX5001]
M49000000L(AM49DL322BGB)@FBGA73 [DX5001]
M49000000M(AM49DL322BGB)@FBGA73 [DX5001]
M49000000N(AM49DL323BGT)@FBGA73 [DX5001]
M490000000(AM49DL323BGT)@FBGA73 [DX5001]
M49000000P(AM49DL323BGB)@FBGA73 [DX5001]
M49000000Q(AM49DL323BGB)@FBGA73 [DX5001]
M49000000R(AM49DL324BGT)@FBGA73 [DX5001]
M49000000S(AM49DL324BGT)@FBGA73 [DX5001]
M49000000T(AM49DL324BGB)@FBGA73 [DX5001]
M49000000U(AM49DL324BGB)@FBGA73 [DX5001]
M49000001A(AM49DL320BGB)@FBGA73 [DX5001]
M49000001B(AM49DL320BGB)@FBGA73 [DX5001]
M49000001Y(AM49PDL640AG)@FBGA73 [DX5072]
M49000001Z(AM49PDL640AG)@FBGA73 [DX5072]
M490000025(AM49DL640AG)@FBGA73 [DX5001]
M490000026(AM49DL640AG)@FBGA73 [DX5001]
M490000028(AM49PDL127BH)@FBGA73 [DX5001]
M490000029(AM49PDL127BH)@FBGA73 [DX5001]
M49000002I(AM49PDL127AH)@FBGA73 [DX5001]
M49000002J(AM49PDL127AH)@FBGA73 [DX5001]
M49000002T(AM49LV6408MT)@FBGA69 [DX5005]
M49000002U(AM49LV6408MB)@FBGA69 [DX5005]
M49000002V(AM49LV6408MT)@FBGA69 [DX5005]
M49000002X(AM49LV6408MB)@FBGA69 [DX5005]
M490000030(AM49PDL129BH)@FBGA73 [DX5001]
M490000031(AM49PDL129BH)@FBGA73 [DX5001]
M490000032(AM49DL3208GB)@FBGA69 [DX5001]
M490000032(AM49DL3208GT)@FBGA69 [DX5005]
M490000034(AM49DL3208GT)@FBGA69 [DX5005]
M490000035(AM49DL3208GB)@FBGA69 [DX5001]
M49000003A(AM49DL640BH)@FBGA73 [DX5001]
M49000003B(AM49DL640BH)@FBGA73 [DX5001]
M49000003C(AM49DL640BH)@FBGA73 [DX5001]
M49000003D(AM49DL640AH)@FBGA73 [DX5001]
M49000003E(AM49DL640AH)@FBGA73 [DX5001]
M49000003F(AM49DL6408H)@FBGA73 [DX5001]
M49000003G(AM49DL6408H)@FBGA73 [DX5001]
M49000003H(AM49DL6408H)@FBGA73 [DX5001]
M49000003I(AM49DL6408H)@FBGA73 [DX5001]

M49000003J(AM49DL640AH)@FBGA73 [DX5001]
M49000003X(AM49DL6408H)@FBGA73 [DX5001]
M49000003Y(AM49DL6408H)@FBGA73 [DX5001]
M49000003Z(AM49LV6408MT)@FBGA69 [DX5005]
M49000004A(AM49LV6408MB)@FBGA69 [DX5005]
M49000004B(AM49BDS640AH)@FBGA89 [DX5005]
M49000004C(AM49BDS640AH)@FBGA89 [DX5005]
M49000004D(AM49BDS640AH)@FBGA89 [DX5005]
M49000004E(AM49BDS640AH)@FBGA89 [DX5005]
M49000004H(AM49LV128BMH)@FBGA64 [DX5054]
M49000004J(AM49LV128BML)@FBGA64 [DX5054]
M49000004K(AM49LV128BMH)@FBGA64 [DX5054]
M49000004L(AM49LV128BML)@FBGA64 [DX5054]
M49000004S(AM49LV128BMaH)@FBGA64 [DX5054]
M49000004T(AM49LV128BMaL)@FBGA64 [DX5054]
M49000004U(AM49LV128BMaH)@FBGA64 [DX5054]
M49000004V(AM49LV128BMaL)@FBGA64 [DX5054]
M4900000K(AM49PDL129AH)@FBGA73 [DX5001]
M4900000L(AM49PDL129AH)@FBGA73 [DX5001]
M500000000(AM50DL128BG)@FBGA73 [DX5001]
M500000001(AM50DL128BG)@FBGA73 [DX5001]
M500000008(AM50DL128CG)@FBGA88 [DX5001]
M500000009(AM50DL128CG)@FBGA88 [DX5001]
M50000004J(AM50DL128BH)@FBGA73 [DX5001]
M50000004K(AM50DL128BH)@FBGA73 [DX5001]
M50000004L(AM50DL128BH)@FBGA73 [DX5001]
M50000004M(AM50DL128CH)@FBGA88 [DX5001]
M50000004N(AM50DL128CH)@FBGA88 [DX5001]
M50000004P(AM50DL128CH)@FBGA88 [DX5001]
M550000000(AM55DL128C8G)@FBGA93 [DX5028]
M550000001(AM55DL128C8G)@FBGA93 [DX5028]
MB84VD21081@FBGA61 [DX5048]
MB84VD21081EA@FBGA56 [DX5045]
MB84VD21081EM@FBGA56 [DX5045]
MB84VD21082@FBGA61 [DX5048]
MB84VD21082EA@FBGA56 [DX5045]
MB84VD21082EM@FBGA56 [DX5045]
MB84VD21083@FBGA61 [DX5048]
MB84VD21083EA@FBGA56 [DX5045]
MB84VD21083EM@FBGA56 [DX5045]
MB84VD21084@FBGA61 [DX5048]
MB84VD21084EA@FBGA56 [DX5045]
MB84VD21084EM@FBGA56 [DX5045]
MB84VD21091@FBGA61 [DX5048]
MB84VD21091EA@FBGA56 [DX5045]
MB84VD21091EM@FBGA56 [DX5045]
MB84VD21092@FBGA61 [DX5048]
MB84VD21092EA@FBGA56 [DX5045]
MB84VD21092EM@FBGA56 [DX5045]
MB84VD21093@FBGA61 [DX5048]
MB84VD21093EA@FBGA56 [DX5045]
MB84VD21093EM@FBGA56 [DX5045]
MB84VD21094@FBGA61 [DX5048]
MB84VD21094EA@FBGA56 [DX5045]
MB84VD21094EM@FBGA56 [DX5045]
MB84VD21181DA@FBGA69 [DX5001]
MB84VD21181EG@FBGA56 [DX5045]
MB84VD21181EM@FBGA56 [DX5045]
MB84VD21182DA@FBGA69 [DX5001]
MB84VD21182EG@FBGA56 [DX5045]
MB84VD21182EM@FBGA56 [DX5045]
MB84VD21183DA@FBGA69 [DX5001]
MB84VD21183EG@FBGA56 [DX5045]
MB84VD21183EM@FBGA56 [DX5045]
MB84VD21184DA@FBGA69 [DX5001]

MB84VD21184EG@FBGA56 [DX5045]　　MB84VD21184EM@FBGA56 [DX5045]
MB84VD21191DA@FBGA69 [DX5001]　　MB84VD21191EG@FBGA56 [DX5045]
MB84VD21191EM@FBGA56 [DX5045]　　MB84VD21192DA@FBGA69 [DX5001]
MB84VD21192EG@FBGA56 [DX5045]　　MB84VD21192EM@FBGA56 [DX5045]
MB84VD21193DA@FBGA69 [DX5001]　　MB84VD21193EG@FBGA56 [DX5045]
MB84VD21193EM@FBGA56 [DX5045]　　MB84VD21194DA@FBGA69 [DX5001]
MB84VD21194EG@FBGA56 [DX5045]　　MB84VD21194EM@FBGA56 [DX5045]
MB84VD22180FA@FBGA59 [DX5045]　　MB84VD22180FM@FBGA59 [DX5045]
MB84VD22181EB@FBGA73 [DX5001]　　MB84VD22181EC@FBGA73 [DX5001]
MB84VD22181EE@FBGA73 [DX5001]　　MB84VD22181FM@FBGA56 [DX5045]
MB84VD22182EB@FBGA73 [DX5001]　　MB84VD22182EC@FBGA73 [DX5001]
MB84VD22182EE@FBGA73 [DX5001]　　MB84VD22183EB@FBGA73 [DX5001]
MB84VD22183EC@FBGA73 [DX5001]　　MB84VD22183EE@FBGA73 [DX5001]
MB84VD22184EB@FBGA73 [DX5001]　　MB84VD22184EC@FBGA73 [DX5001]
MB84VD22184EE@FBGA73 [DX5001]　　MB84VD22184FM@FBGA56 [DX5045]
MB84VD22190FA@FBGA59 [DX5045]　　MB84VD22190FM@FBGA59 [DX5045]
MB84VD22191EB@FBGA73 [DX5001]　　MB84VD22191EC@FBGA73 [DX5001]
MB84VD22191EE@FBGA73 [DX5001]　　MB84VD22191FM@FBGA56 [DX5045]
MB84VD22192EB@FBGA73 [DX5001]　　MB84VD22192EC@FBGA73 [DX5001]
MB84VD22192EE@FBGA73 [DX5001]　　MB84VD22193EB@FBGA73 [DX5001]
MB84VD22193EC@FBGA73 [DX5001]　　MB84VD22193EE@FBGA73 [DX5001]
MB84VD22194EB@FBGA73 [DX5001]　　MB84VD22194EC@FBGA73 [DX5001]
MB84VD22194EE@FBGA73 [DX5001]　　MB84VD22194FM@FBGA56 [DX5045]
MB84VD22280FA@FBGA59 [DX5045]　　MB84VD22280FE@FBGA59 [DX5045]
MB84VD22282EA@FBGA71 [DX5001]　　MB84VD22282EE@FBGA71 [DX5001]
MB84VD22283EA@FBGA71 [DX5001]　　MB84VD22283EE@FBGA71 [DX5001]
MB84VD22284EA@FBGA71 [DX5001]　　MB84VD22284EE@FBGA71 [DX5001]
MB84VD22290FA@FBGA59 [DX5045]　　MB84VD22290FE@FBGA59 [DX5045]
MB84VD22292EA@FBGA71 [DX5001]　　MB84VD22292EE@FBGA71 [DX5001]
MB84VD22293EA@FBGA71 [DX5001]　　MB84VD22293EE@FBGA71 [DX5001]
MB84VD22294EA@FBGA71 [DX5001]　　MB84VD22294EE@FBGA71 [DX5001]
MB84VD22386EJ@FBGA71 [DX5001]　　MB84VD22387EJ@FBGA71 [DX5001]
MB84VD22388EJ@FBGA71 [DX5001]　　MB84VD22396EJ@FBGA71 [DX5001]
MB84VD22397EJ@FBGA71 [DX5001]　　MB84VD22398EJ@FBGA71 [DX5001]
MB84VD23180FM@FBGA73 [DX5001]　　MB84VD23280EA@FBGA101 [DX5076]
MB84VD23280EE@FBGA101 [DX5076]　　MB84VD23280FA@FBGA65 [DX5048]
MB84VD23381EJ@FBGA101 [DX5076]　　MB84VD23381FJ@FBGA65 [DX5048]
MB84VD23381HJ@FBGA56 [DX5045]　　MB84VD23481FJ@FBGA65 [DX5048]
MB84VD23581FJ@FBGA65 [DX5048]　　MB84VP23481FK@FBGA65 [DX5048]
MB84VP24481HK@FBGA73 [DX5001]　　MB84VP24491HK@FBGA73 [DX5001]
MBM29DL161BD(REVERSE)@TSOP48 [DX1004]
MBM29DL161BD@FBGA48 [DX5002]　　MBM29DL161BD@TSOP48 [DX1004]
MBM29DL161BE(REVERSE)@TSOP48 [DX1004]
MBM29DL161BE@FBGA48 [DX5002]　　MBM29DL161BE@TSOP48 [DX1004]
MBM29DL161TD(REVERSE)@TSOP48 [DX1004]
MBM29DL161TD@FBGA48 [DX5002]　　MBM29DL161TD@TSOP48 [DX1004]
MBM29DL161TE(REVERSE)@TSOP48 [DX1004]
MBM29DL161TE@FBGA48 [DX5002]　　MBM29DL161TE@TSOP48 [DX1004]

MBM29DL162BD(REVERSE)@TSOP48 [DX1004]
MBM29DL162BD@FBGA48 [DX5002]　　MBM29DL162BD@TSOP48 [DX1004]
MBM29DL162BE(REVERSE)@TSOP48 [DX1004]
MBM29DL162BE@FBGA48 [DX5002]　　MBM29DL162BE@TSOP48 [DX1004]
MBM29DL162TD(REVERSE)@TSOP48 [DX1004]
MBM29DL162TD@FBGA48 [DX5002]　　MBM29DL162TD@TSOP48 [DX1004]
MBM29DL162TE(REVERSE)@TSOP48 [DX1004]
MBM29DL162TE@FBGA48 [DX5002]　　MBM29DL162TE@TSOP48 [DX1004]
MBM29DL163BD(REVERSE)@TSOP48 [DX1004]
MBM29DL163BD@FBGA48 [DX5002]　　MBM29DL163BD@TSOP48 [DX1004]
MBM29DL163BE(REVERSE)@TSOP48 [DX1004]
MBM29DL163BE@FBGA48 [DX5002]　　MBM29DL163BE@TSOP48 [DX1004]
MBM29DL163TD(REVERSE)@TSOP48 [DX1004]
MBM29DL163TD@FBGA48 [DX5002]　　MBM29DL163TD@TSOP48 [DX1004]
MBM29DL163TE(REVERSE)@TSOP48 [DX1004]
MBM29DL163TE@FBGA48 [DX5002]　　MBM29DL163TE@TSOP48 [DX1004]
MBM29DL164BD(REVERSE)@TSOP48 [DX1004]
MBM29DL164BD@FBGA48 [DX5002]　　MBM29DL164BD@TSOP48 [DX1004]
MBM29DL164BE(REVERSE)@TSOP48 [DX1004]
MBM29DL164BE@FBGA48 [DX5002]　　MBM29DL164BE@TSOP48 [DX1004]
MBM29DL164TD(REVERSE)@TSOP48 [DX1004]
MBM29DL164TD@FBGA48 [DX5002]　　MBM29DL164TD@TSOP48 [DX1004]
MBM29DL164TE(REVERSE)@TSOP48 [DX1004]
MBM29DL164TE@FBGA48 [DX5002]　　MBM29DL164TE@TSOP48 [DX1004]
MBM29DL320BF@FBGA48 [DX5039]　　MBM29DL320BF@TSOP48 [DX1004]
MBM29DL320TF@FBGA48 [DX5039]　　MBM29DL320TF@TSOP48 [DX1004]
MBM29DL321BD(REVERSE)@TSOP48 [DX1004]
MBM29DL321BD@FBGA63 [DX5047]　　MBM29DL321BD@TSOP48 [DX1004]
MBM29DL321BE(REVERSE)@TSOP48 [DX1004]
MBM29DL321BE@FBGA63 [DX5047]　　MBM29DL321BE@TSOP48 [DX1004]
MBM29DL321TD(REVERSE)@TSOP48 [DX1004]
MBM29DL321TD@FBGA63 [DX5047]　　MBM29DL321TD@TSOP48 [DX1004]
MBM29DL321TE(REVERSE)@TSOP48 [DX1004]
MBM29DL321TE@FBGA63 [DX5047]　　MBM29DL321TE@TSOP48 [DX1004]
MBM29DL322BD(REVERSE)@TSOP48 [DX1004]
MBM29DL322BD@FBGA63 [DX5047]　　MBM29DL322BD@TSOP48 [DX1004]
MBM29DL322BE(REVERSE)@TSOP48 [DX1004]
MBM29DL322BE@FBGA63 [DX5047]　　MBM29DL322BE@TSOP48 [DX1004]
MBM29DL322TD(REVERSE)@TSOP48 [DX1004]
MBM29DL322TD@FBGA63 [DX5047]　　MBM29DL322TD@TSOP48 [DX1004]
MBM29DL322TE(REVERSE)@TSOP48 [DX1004]
MBM29DL322TE@FBGA63 [DX5047]　　MBM29DL322TE@TSOP48 [DX1004]
MBM29DL323BD(REVERSE)@TSOP48 [DX1004]
MBM29DL323BD@FBGA63 [DX5047]　　MBM29DL323BD@TSOP48 [DX1004]
MBM29DL323BE(REVERSE)@TSOP48 [DX1004]
MBM29DL323BE@FBGA63 [DX5047]　　MBM29DL323BE@TSOP48 [DX1004]
MBM29DL323BF@FBGA48 [DX5039]　　MBM29DL323BF@TSOP48 [DX1004]
MBM29DL323TD(REVERSE)@TSOP48 [DX1004]

MBM29DL323TD@FBGA63 [DX5047]
MBM29DL323TD@TSOP48 [DX1004]
MBM29DL323TE(REVERSE)@TSOP48 [DX1004]
MBM29DL323TE@FBGA63 [DX5047]
MBM29DL323TE@TSOP48 [DX1004]
MBM29DL323TF@FBGA48 [DX5039]
MBM29DL323TF@TSOP48 [DX1004]
MBM29DL324BD(REVERSE)@TSOP48 [DX1004]
MBM29DL324BD@FBGA63 [DX5047]
MBM29DL324BD@TSOP48 [DX1004]
MBM29DL324BE(REVERSE)@TSOP48 [DX1004]
MBM29DL324BE@FBGA63 [DX5047]
MBM29DL324BE@TSOP48 [DX1004]
MBM29DL324TD(REVERSE)@TSOP48 [DX1004]
MBM29DL324TD@FBGA63 [DX5047]
MBM29DL324TD@TSOP48 [DX1004]
MBM29DL324TE(REVERSE)@TSOP48 [DX1004]
MBM29DL324TE@FBGA63 [DX5047]
MBM29DL324TE@TSOP48 [DX1004]
MBM29DL32BF@FBGA48 [DX5039]
MBM29DL32BF@TSOP48 [DX1004]
MBM29DL32TF@FBGA48 [DX5039]
MBM29DL32TF@TSOP48 [DX1004]
MBM29DL34BF@FBGA48 [DX5039]
MBM29DL34BF@TSOP48 [DX1004]
MBM29DL34TF@FBGA48 [DX5039]
MBM29DL34TF@TSOP48 [DX1004]
MBM29DL400BB@PSOP44 [DX1014]
MBM29DL400BB@TSOP48 [DX1004]
MBM29DL400BC(REVERSE)@TSOP48 [DX1004]
MBM29DL400BC@PSOP44 [DX1014]
MBM29DL400BC@TSOP48 [DX1004]
MBM29DL400BT@PSOP44 [DX1014]
MBM29DL400BT@TSOP48 [DX1004]
MBM29DL400TC(REVERSE)@TSOP48 [DX1004]
MBM29DL400TC@PSOP44 [DX1014]
MBM29DL400TC@TSOP48 [DX1004]
MBM29DL640E(REVERSE)@TSOP48 [DX1004]
MBM29DL640E@FBGA63 [DX5041]
MBM29DL640E@TSOP48 [DX1004]
MBM29DL64DF@FBGA48 [DX5022]
MBM29DL64DF@TSOP48 [DX1004]
MBM29DL800B@PSOP44 [DX1014]
MBM29DL800B@TSOP48 [DX1004]
MBM29DL800BA(REVERSE)@TSOP48 [DX1004]
MBM29DL800BA@FBGA48 [DX5039]
MBM29DL800BA@PSOP44 [DX1014]
MBM29DL800BA@TSOP48 [DX1004]
MBM29DL800BB@PSOP44 [DX1014]
MBM29DL800BB@TSOP48 [DX1004]
MBM29DL800BT@PSOP44 [DX1014]
MBM29DL800BT@TSOP48 [DX1004]
MBM29DL800T@PSOP44 [DX1014]
MBM29DL800T@TSOP48 [DX1004]
MBM29DL800TA(REVERSE)@TSOP48 [DX1004]
MBM29DL800TA@FBGA48 [DX5039]
MBM29DL800TA@PSOP44 [DX1014]
MBM29DL800TA@TSOP48 [DX1004]
MBM29DS163BE@FBGA48 [DX5043]
MBM29DS163BE@TSOP48 [DX1004]
MBM29DS163TE@FBGA48 [DX5043]
MBM29DS163TE@TSOP48 [DX1004]
MBM29F001B [DX0001]
MBM29F001B@PLCC32 [DX2032]
MBM29F001B@TSOP32 [DX1002]
MBM29F001T [DX0001]
MBM29F001T@PLCC32 [DX2032]
MBM29F001T@TSOP32 [DX1002]
MBM29F002B [DX0001]
MBM29F002B@PLCC32 [DX2032]
MBM29F002B@TSOP32 [DX1002]
MBM29F002NB [DX0001]
MBM29F002NB@PLCC32 [DX2032]
MBM29F002NB@TSOP32 [DX1002]
MBM29F002NT [DX0001]
MBM29F002NT@PLCC32 [DX2032]
MBM29F002NT@TSOP32 [DX1002]
MBM29F002T [DX0001]
MBM29F002T@PLCC32 [DX2032]
MBM29F002T@TSOP32 [DX1002]
MBM29F010 [DX0001]
MBM29F010@PLCC32 [DX2032]
MBM29F010@TSOP32 [DX1002]
MBM29F010A [DX0001]
MBM29F010A@PLCC32 [DX2032]

MBM29F010A@TSOP32 [DX1002]
MBM29F016@PSOP44 [DX1014]
MBM29F016@TSOP40 [DX1006]
MBM29F016@TSOP48 [DX1004]
MBM29F016A@PSOP44 [DX1014]
MBM29F016A@TSOP40 [DX1006]
MBM29F016A@TSOP48 [DX1004]
MBM29F016B@PSOP44 [DX1014]
MBM29F016B@TSOP40 [DX1006]
MBM29F016B@TSOP48 [DX1004]
MBM29F017A(REVERSE)@TSOP48 [DX1004]
MBM29F017A@TSOP48 [DX1004]
MBM29F017B@TSOP48 [DX1004]
MBM29F017D@TSOP40 [DX1006]
MBM29F017D@TSOP48 [DX1004]
MBM29F032B@PSOP44 [DX1014]
MBM29F032B@TSOP40 [DX1006]
MBM29F033C@TSOP40 [DX1006]
MBM29F040 [DX0001]
MBM29F040@PLCC32 [DX2032]
MBM29F040@TSOP32 [DX1002]
MBM29F040B [DX0001]
MBM29F040B@PLCC32 [DX2032]
MBM29F040B@TSOP32 [DX1002]
MBM29F040C@PLCC32 [DX2032]
MBM29F040C@TSOP32 [DX1002]
MBM29F080@PSOP44 [DX1014]
MBM29F080@TSOP40 [DX1006]
MBM29F080A(REVERSE)@TSOP40 [DX1006]
MBM29F080A(REVERSE)@TSOP48 [DX1004]
MBM29F080A@PSOP44 [DX1014]
MBM29F080A@TSOP40 [DX1006]
MBM29F080A@TSOP48 [DX1004]
MBM29F080B@PSOP44 [DX1014]
MBM29F080B@TSOP40 [DX1006]
MBM29F100B@PSOP44 [DX1014]
MBM29F100B@TSOP48 [DX1004]
MBM29F100T@PSOP44 [DX1014]
MBM29F100T@TSOP48 [DX1004]
MBM29F160BE(REVERSE)@TSOP48 [DX1004]
MBM29F160BE@TSOP48 [DX1004]
MBM29F160TE(REVERSE)@TSOP48 [DX1004]
MBM29F160TE@TSOP48 [DX1004]
MBM29F200AB@PSOP44 [DX1014]
MBM29F200AB@TSOP48 [DX1004]
MBM29F200AT@PSOP44 [DX1014]
MBM29F200AT@TSOP48 [DX1004]
MBM29F200B@PSOP44 [DX1014]
MBM29F200B@TSOP48 [DX1004]
MBM29F200BC(REVERSE)@TSOP48 [DX1004]
MBM29F200BC@PSOP44 [DX1014]
MBM29F200BC@TSOP48 [DX1004]
MBM29F200T@PSOP44 [DX1014]
MBM29F200T@TSOP48 [DX1004]
MBM29F200TC(REVERSE)@TSOP48 [DX1004]
MBM29F200TC@PSOP44 [DX1014]
MBM29F200TC@TSOP48 [DX1004]
MBM29F400AB@PSOP44 [DX1014]
MBM29F400AB@TSOP48 [DX1004]
MBM29F400AT@PSOP44 [DX1014]
MBM29F400AT@TSOP48 [DX1004]
MBM29F400B@PSOP44 [DX1014]
MBM29F400B@TSOP48 [DX1004]
MBM29F400BB@PSOP44 [DX1014]
MBM29F400BB@TSOP48 [DX1004]
MBM29F400BC(REVERSE)@TSOP48 [DX1004]
MBM29F400BC@PSOP44 [DX1014]
MBM29F400BC@TSOP48 [DX1004]
MBM29F400BT@PSOP44 [DX1014]
MBM29F400BT@TSOP48 [DX1004]
MBM29F400T@PSOP44 [DX1014]
MBM29F400T@TSOP48 [DX1004]
MBM29F400TC(REVERSE)@TSOP48 [DX1004]
MBM29F400TC@PSOP44 [DX1014]
MBM29F400TC@TSOP48 [DX1004]
MBM29F800B@PSOP44 [DX1014]
MBM29F800B@TSOP48 [DX1004]
MBM29F800BA(REVERSE)@TSOP48 [DX1004]
MBM29F800BA@PSOP44 [DX1014]
MBM29F800BA@TSOP48 [DX1004]
MBM29F800BB@PSOP44 [DX1014]
MBM29F800BB@TSOP48 [DX1004]

MBM29F800BT@PSOP44 [DX1014]　　MBM29F800BT@TSOP48 [DX1004]
MBM29F800T@PSOP44 [DX1014]　　MBM29F800T@TSOP48 [DX1004]
MBM29F800TA(REVERSE)@TSOP48 [DX1004]
MBM29F800TA@PSOP44 [DX1014]　　MBM29F800TA@TSOP48 [DX1004]
MBM29LL800B@TSOP48 [DX1004]　　MBM29LL800BB@TSOP48 [DX1004]
MBM29LL800BT@TSOP48 [DX1004]　　MBM29LL800T@TSOP48 [DX1004]
MBM29LV001B@PLCC32 [DX2032]
MBM29LV001BB(REVERSE)@TSOP32 [DX1002]
MBM29LV001BB@PLCC32 [DX2032]　　MBM29LV001BB@TSOP32 [DX1002]
MBM29LV001BC(REVERSE)@TSOP32 [DX1002]
MBM29LV001BC@PLCC32 [DX2032]　　MBM29LV001BC@TSOP32 [DX1002]
MBM29LV001BT(REVERSE)@TSOP32 [DX1002]
MBM29LV001BT@PLCC32 [DX2032]　　MBM29LV001BT@TSOP32 [DX1002]
MBM29LV001T@TSOP32 [DX1002]
MBM29LV001TC(REVERSE)@TSOP32 [DX1002]
MBM29LV001TC@PLCC32 [DX2032]　　MBM29LV001TC@TSOP32 [DX1002]
MBM29LV002B@TSOP40 [DX1006]　　MBM29LV002T@TSOP40 [DX1006]
MBM29LV004B@TSOP40 [DX1006]　　MBM29LV004BB@TSOP40 [DX1006]
MBM29LV004BT@TSOP40 [DX1006]　　MBM29LV004T@TSOP40 [DX1006]
MBM29LV008B@TSOP40 [DX1006]　　MBM29LV008BB@TSOP40 [DX1006]
MBM29LV008BT@TSOP40 [DX1006]　　MBM29LV008T@TSOP40 [DX1006]
MBM29LV016/B@TSOP40 [DX1006]　　MBM29LV016/T@TSOP40 [DX1006]
MBM29LV016B@TSOP40 [DX1006]　　MBM29LV017@FBGA48 [DX5022]
MBM29LV017@TSOP40 [DX1006]　　MBM29LV017B@TSOP40 [DX1006]
MBM29LV017E@TSOP40 [DX1006]　　MBM29LV033C@TSOP40 [DX1006]
MBM29LV080@TSOP40 [DX1006]　　MBM29LV080A@TSOP40 [DX1006]
MBM29LV081@TSOP40 [DX1006]　　MBM29LV081B@TSOP40 [DX1006]
MBM29LV116B@TSOP40 [DX1006]
MBM29LV160B(REVERSE)@TSOP48 [DX1004]
MBM29LV160B@FBGA48 [DX5022]　　MBM29LV160B@TSOP48 [DX1004]
MBM29LV160BE(REVERSE)@TSOP48 [DX1004]
MBM29LV160BE@FBGA48 [DX5002]　　MBM29LV160BE@PSOP44 [DX1014]
MBM29LV160BE@TSOP48 [DX1004]　　MBM29LV160BM@FBGA48 [DX5002]
MBM29LV160BM@TSOP48 [DX1004]
MBM29LV160T(REVERSE)@TSOP48 [DX1004]
MBM29LV160T@FBGA48 [DX5022]　　MBM29LV160T@TSOP48 [DX1004]
MBM29LV160TE(REVERSE)@TSOP48 [DX1004]
MBM29LV160TE@FBGA48 [DX5002]　　MBM29LV160TE@PSOP44 [DX1014]
MBM29LV160TE@TSOP48 [DX1004]　　MBM29LV160TM@FBGA48 [DX5002]
MBM29LV160TM@TSOP48 [DX1004]　　MBM29LV200B@PSOP44 [DX1014]
MBM29LV200B@TSOP48 [DX1004]　　MBM29LV200BB@PSOP44 [DX1014]
MBM29LV200BB@TSOP48 [DX1004]
MBM29LV200BC(REVERSE)@TSOP48 [DX1004]
MBM29LV200BC@PSOP44 [DX1014]　　MBM29LV200BC@TSOP48 [DX1004]
MBM29LV200BT@PSOP44 [DX1014]　　MBM29LV200BT@TSOP48 [DX1004]
MBM29LV200T@PSOP44 [DX1014]　　MBM29LV200T@TSOP48 [DX1004]
MBM29LV200TC(REVERSE)@TSOP48 [DX1004]
MBM29LV200TC@PSOP44 [DX1014]　　MBM29LV200TC@TSOP48 [DX1004]

MBM29LV320BE(REVERSE)@TSOP48 [DX1004]
MBM29LV320BE@FBGA63 [DX5063]
MBM29LV320BE@TSOP48 [DX1004]
MBM29LV320TE(REVERSE)@TSOP48 [DX1004]
MBM29LV320TE@FBGA63 [DX5063]
MBM29LV320TE@TSOP48 [DX1004]
MBM29LV400B@PSOP44 [DX1014]
MBM29LV400B@TSOP48 [DX1004]
MBM29LV400BB@PSOP44 [DX1014]
MBM29LV400BB@TSOP48 [DX1004]
MBM29LV400BC@FBGA48 [DX5002]
MBM29LV400BC@PSOP44 [DX1014]
MBM29LV400BC@TSOP48 [DX1004]
MBM29LV400BT@PSOP44 [DX1014]
MBM29LV400BT@TSOP48 [DX1004]
MBM29LV400T@PSOP44 [DX1014]
MBM29LV400T@TSOP48 [DX1004]
MBM29LV400TC@FBGA48 [DX5002]
MBM29LV400TC@PSOP44 [DX1014]
MBM29LV400TC@TSOP48 [DX1004]
MBM29LV650UE(REVERSE)@TSOP48 [DX1004]
MBM29LV650UE@TSOP48 [DX1004]
MBM29LV651UE(REVERSE)@TSOP48 [DX1004]
MBM29LV651UE@TSOP48 [DX1004]
MBM29LV652UE@FGBA63 [DX5041]
MBM29LV800B@PSOP44 [DX1014]
MBM29LV800B@TSOP48 [DX1004]
MBM29LV800BA(REVERSE)@TSOP48 [DX1004]
MBM29LV800BA@FBGA48 [DX5039]
MBM29LV800BA@PSOP44 [DX1014]
MBM29LV800BA@TSOP48 [DX1004]
MBM29LV800BB@PSOP44 [DX1014]
MBM29LV800BB@TSOP48 [DX1004]
MBM29LV800BE(REVERSE)@TSOP48 [DX1004]
MBM29LV800BE@FBGA48 [DX5039]
MBM29LV800BE@PSOP44 [DX1014]
MBM29LV800BE@TSOP48 [DX1004]
MBM29LV800BT@PSOP44 [DX1014]
MBM29LV800BT@TSOP48 [DX1004]
MBM29LV800T@PSOP44 [DX1014]
MBM29LV800T@TSOP48 [DX1004]
MBM29LV800TA(REVERSE)@TSOP48 [DX1004]
MBM29LV800TA@FBGA48 [DX5039]
MBM29LV800TA@PSOP44 [DX1014]
MBM29LV800TA@TSOP48 [DX1004]
MBM29LV800TE(REVERSE)@TSOP48 [DX1004]
MBM29LV800TE@FBGA48 [DX5039]
MBM29LV800TE@PSOP44 [DX1014]
MBM29LV800TE@TSOP48 [DX1004]
MBM29PDS323B@FBGA63 [DX5047]
MBM29PDS323T@FBGA63 [DX5047]
MBM29PL12LM@TSOP56 [DX1011]
MBM29PL160BD@PSOP44 [DX1014]
MBM29PL160BD@TSOP48 [DX1004]
MBM29PL160TD@PSOP44 [DX1014]
MBM29PL160TD@TSOP48 [DX1004]
MBM29PL32BM@FBGA48 [DX5002]
MBM29PL32BM@TSOP48 [DX1004]
MBM29PL32TM@FBGA48 [DX5002]
MBM29PL32TM@TSOP48 [DX1004]
MBM29PL64LM@TSOP48 [DX1004]
MBM29PL64LM@TSOP56 [DX1011]
MBM29PL65LM@TSOP48 [DX1004]
MBM29QM12DH@FBGA80 [DX5001]
MBM29QM12DH@TSOP56 [DX1011]
MBM29SL160BD(REVERSE)@TSOP48 [DX1004]
MBM29SL160BD@FBGA48 [DX5022]
MBM29SL160BD@TSOP48 [DX1004]
MBM29SL160TD(REVERSE)@TSOP48 [DX1004]
MBM29SL160TD@FBGA48 [DX5022]
MBM29SL160TD@TSOP48 [DX1004]
MBM29SL800BD(REVERSE)@TSOP48 [DX1004]
MBM29SL800BD@FBGA48 [DX5022]
MBM29SL800BD@TSOP48 [DX1004]
MBM29SL800BE@FBGA48 [DX5043]
MBM29SL800TD(REVERSE)@TSOP48 [DX1004]
MBM29SL800TD@FBGA48 [DX5002]
MBM29SL800TD@TSOP48 [DX1004]

MBM29SL800TE@FBGA48 [DX5043]
MSP55LV128(fast)@PSOP44 [DX1014]
MSP55LV128@PSOP44 [DX1014]
MSP55LV128T(*8)@TSOP56 [DX1011]
MSP55LV128T(fast)@PSOP44 [DX1014]
MSP55LV128T@PSOP44 [DX1014]
MSP55LV128T@TSOP56 [DX1011]
MSP55LV160@PSOP44 [DX1014]
MSP55LV160A@PSOP44 [DX1014]
MSP55LV512@SSOP70 [DX1057]
MSP55LV650@PSOP44 [DX1014]
PDL127H53V(AM29PDL127H53)@FBGA80 [DX5053]
PDL127H63V(AM29PDL127H63)@FBGA80 [DX5053]
PDL127H68V(AM29PDL127H68)@FBGA80 [DX5053]
PDL127H88V(AM29PDL127H88)@FBGA80 [DX5053]
PDL129H53V(AM29PDL129H53)@FBGA80 [DX5053]
PDL129H63V(AM29PDL129H63)@FBGA80 [DX5053]
PDL129H68V(AM29PDL129H68)@FBGA80 [DX5053]
PDL129H88V(AM29PDL129H88)@FBGA80 [DX5053]
S19GL016ATFA00F0@TSOP48 [DX1004]
S19GL032ATFA00F0@TSOP48 [DX1004]
S19MN02GP30TFP00@TSOP48 [DX1004]
S25FL001D@SOIC8 [DX1045]
S25FL001D@USON8 [DX4005]
S25FL002A@SOIC8 [DX1044#1]
S25FL002A@USON8 [DX4005#1]
S25FL002D@SOIC8 [DX1045#1]
S25FL002D@USON8 [DX4005#1]
S25FL004A@SOIC8 [DX1044#1]
S25FL004A@USON8 [DX4005#1]
S25FL004D@SOIC8 [DX1045#1]
S25FL004D@USON8 [DX4005#1]
S25FL004K@SOIC8(150 mil) [DX1045#1]
S25FL004K@SOIC8(208 mil) [DX1044#1]
S25FL008A@SOIC8 [DX1044#1]
S25FL008A@USON8 [DX4005#1]
S25FL008D@SOIC8 [DX1045#1]
S25FL008D@USON8 [DX4005#1]
S25FL008K@SOIC8(150 mil) [DX1045#1]
S25FL008K@SOIC8(208 mil) [DX1044#1]
S25FL016A@SOIC16 [DX1072#1]
S25FL016A@SOIC16(ISP) [DX0001]
S25FL016A@SOIC16(Normal mode) [DX1033#1]
S25FL016A@SOIC8 [DX1044#1]
S25FL016A@SOIC8(ISP) [DX0001]
S25FL016A@SOIC8(Normal mode) [DX1044#1]
S25FL016A@WSON8 [DX4006#1]
S25FL016A@WSON8(ISP) [DX0001]
S25FL016A@WSON8(Normal mode) [DX4006#1]
S25FL016K@SOIC16 [DX1072#1]
S25FL016K@SOIC8(150 mil) [DX1045#1]
S25FL016K@SOIC8(208 mil) [DX1044#1]
S25FL020A@SOIC8(4.0) [DX1045#1]
S25FL020A@SOIC8(5.4) [DX1044#1]
S25FL020A@USON8 [DX4005#1]
S25FL032A@SOIC16 [DX1072#1]
S25FL032A@SOIC16(ISP) [DX0001]
S25FL032A@SOIC16(Normal mode) [DX1033#1]
S25FL032A@WSON8 [DX4006#1]
S25FL032A@WSON8(ISP) [DX0001]
S25FL032A@WSON8(Normal mode) [DX4006#1]
S25FL032K@SOIC16 [DX1072#1]
S25FL032K@SOIC8(150 mil) [DX1045#1]
S25FL032K@SOIC8(208 mil) [DX1044#1]
S25FL032P@BGA24(5*5 pin) [DX5157]
S25FL032P@BGA24(6*4 pin) [DX5146]
S25FL032P@SOIC16 [DX1072#1]
S25FL032P@SOIC8 [DX1044#1]

S25FL032P@USON8 [DX4005#1]　　S25FL032P@WSON8 [DX4006#1]
S25FL040A(Bottom Boot)@SOP8(4.0) [DX1045#1]
S25FL040A(Bottom Boot)@SOP8(5.4) [DX1044#1]
S25FL040A(Bottom Boot)@USON8 [DX4005#1]
S25FL040A(Top Boot)@SOP8(4.0) [DX1045#1]
S25FL040A(Top Boot)@SOP8(5.4) [DX1044#1]
S25FL040A(Top Boot)@USON8 [DX4005#1]
S25FL040A@SOP8(4.0) [DX1045#1]　　S25FL040A@SOP8(5.4) [DX1044#1]
S25FL040A@USON8 [DX4005#1]　　S25FL064A@SOIC16 [DX1072#1]
S25FL064A@SOIC16(ISP) [DX0001]
S25FL064A@SOIC16(Normal mode) [DX1033#1]
S25FL064A@WSON8 [DX4006#1]　　S25FL064A@WSON8(ISP) [DX0001]
S25FL064A@WSON8(Normal mode) [DX4006#1]
S25FL064K@SOIC16 [DX1072#1]
S25FL064K@SOIC8(150 mil) [DX1045#1]
S25FL064K@SOIC8(208 mil) [DX1044#1]
S25FL064P@BGA24(5*5pin) [DX5157]
S25FL064P@BGA24(5*5pin)(4K bit) [DX5157]
S25FL064P@BGA24(6*4pin) [DX5146]
S25FL064P@BGA24(6*4pin)(4K bit) [DX5146]
S25FL064P@SOIC16 [DX1072#1]
S25FL064P@SOIC16(4K bit) [DX1072#1]
S25FL064P@WSON8 [DX4006#1]
S25FL064P@WSON8(4K bit) [DX4006#1]
S25FL080A@SOIC8(4.0) [DX1045#1]　　S25FL080A@SOIC8(5.4) [DX1044#1]
S25FL080A@USON8 [DX4005#1]　　S25FL116K@BGA24(4*6) [DX5146]
S25FL116K@BGA24(5*5) [DX5157]　　S25FL116K@SOIC8(4.0) [DX1045#1]
S25FL116K@SOIC8(5.4) [DX1044#1]　　S25FL116K@USON8 [DX4005#1]
S25FL127SABBxxC0 [DX5157]　　S25FL127SABBxxD0 [DX5146]
S25FL127SABMxx10 [DX1044#1]　　S25FL127SABNxx10 [DX4005#1]
S25FL128K@SOIC16 [DX1072#1]
S25FL128P(256 KB)@SOIC16 [DX1072#1]
S25FL128P(256 KB)@SOIC16(ISP) [DX0001]
S25FL128P(256 KB)@WSON8 [DX4006#1]
S25FL128P(256 KB)@WSON8(ISP) [DX0001]
S25FL128P(64 KB)@SOIC16 [DX1072#1]
S25FL128P(64 KB)@SOIC16(ISP) [DX0001]
S25FL128P(64 KB)@WSON8 [DX4006#1]
S25FL128P(64 KB)@WSON8(ISP) [DX0001]
S25FL128S(256byte)@BGA24[4*6] [DX5146]
S25FL128S(256byte)@BGA24[5*5] [DX5157]
S25FL128S(256byte)@SOIC16 [DX1033#1]
S25FL128S(256byte)@WSON8 [DX4006#1]
S25FL128S(512byte)@BGA24[4*6] [DX5146]
S25FL128S(512byte)@BGA24[5*5] [DX5157]
S25FL128S(512byte)@SOIC16 [DX1033#1]
S25FL128S(512byte)@WSON8 [DX4006#1]
S25FL128SAGBxx20 [DX5157]　　S25FL128SAGBxx21 [DX5157]

S25FL128SAGBxx30 [DX5146]	S25FL128SAGBxx31 [DX5146]
S25FL128SAGBxx40 [DX5157]	S25FL128SAGBxx41 [DX5157]
S25FL128SAGBxx60 [DX5146]	S25FL128SAGBxx61 [DX5146]
S25FL128SAGBxx70 [DX5157]	S25FL128SAGBxx71 [DX5157]
S25FL128SAGBxx80 [DX5146]	S25FL128SAGBxx81 [DX5146]
S25FL128SAGBxxA0 [DX5157]	S25FL128SAGBxxA1 [DX5157]
S25FL128SAGBxxB0 [DX5146]	S25FL128SAGBxxB1 [DX5146]
S25FL128SAGBxxC0 [DX5157]	S25FL128SAGBxxC1 [DX5157]
S25FL128SAGBxxD0 [DX5146]	S25FL128SAGBxxD1 [DX5146]
S25FL128SAGBxxE0 [DX5157]	S25FL128SAGBxxE1 [DX5157]
S25FL128SAGBxxF0 [DX5146]	S25FL128SAGBxxF1 [DX5146]
S25FL128SAGMxx00 [DX1033#1]	S25FL128SAGMxx01 [DX1033#1]
S25FL128SAGMxx90 [DX1033#1]	S25FL128SAGMxx91 [DX1033#1]
S25FL128SAGMxxG0 [DX1033#1]	S25FL128SAGMxxG1 [DX1033#1]
S25FL128SAGMxxH0 [DX1033#1]	S25FL128SAGMxxH1 [DX1033#1]
S25FL128SAGMxxQ0 [DX1033#1]	S25FL128SAGMxxQ1 [DX1033#1]
S25FL128SAGMxxR0 [DX1033#1]	S25FL128SAGMxxR1 [DX1033#1]
S25FL128SAGNxx00 [DX4006#1]	S25FL128SAGNxx01 [DX4006#1]
S25FL128SAGNxx90 [DX4006#1]	S25FL128SAGNxx91 [DX4006#1]
S25FL128SDPBxx20 [DX5157]	S25FL128SDPBxx21 [DX5157]
S25FL128SDPBxx30 [DX5146]	S25FL128SDPBxx31 [DX5146]
S25FL128SDPBxx40 [DX5157]	S25FL128SDPBxx41 [DX5157]
S25FL128SDPBxx60 [DX5146]	S25FL128SDPBxx61 [DX5146]
S25FL128SDPBxx70 [DX5157]	S25FL128SDPBxx71 [DX5157]
S25FL128SDPBxx80 [DX5146]	S25FL128SDPBxx81 [DX5146]
S25FL128SDPBxxA0 [DX5157]	S25FL128SDPBxxA1 [DX5157]
S25FL128SDPBxxB0 [DX5146]	S25FL128SDPBxxB1 [DX5146]
S25FL128SDPBxxC0 [DX5157]	S25FL128SDPBxxC1 [DX5157]
S25FL128SDPBxxD0 [DX5146]	S25FL128SDPBxxD1 [DX5146]
S25FL128SDPBxxE0 [DX5157]	S25FL128SDPBxxE1 [DX5157]
S25FL128SDPBxxF0 [DX5146]	S25FL128SDPBxxF1 [DX5146]
S25FL128SDPMxx00 [DX1033#1]	S25FL128SDPMxx01 [DX1033#1]
S25FL128SDPMxx90 [DX1033#1]	S25FL128SDPMxx91 [DX1033#1]
S25FL128SDPMxxG0 [DX1033#1]	S25FL128SDPMxxG1 [DX1033#1]
S25FL128SDPMxxH0 [DX1033#1]	S25FL128SDPMxxH1 [DX1033#1]
S25FL128SDPMxxQ0 [DX1033#1]	S25FL128SDPMxxQ1 [DX1033#1]
S25FL128SDPMxxR0 [DX1033#1]	S25FL128SDPMxxR1 [DX1033#1]
S25FL128SDPNxx00 [DX4006#1]	S25FL128SDPNxx01 [DX4006#1]
S25FL128SDPNxx90 [DX4006#1]	S25FL128SDPNxx91 [DX4006#1]
S25FL128SxxBxK0 [DX5157]	S25FL128SxxBxK1 [DX5157]
S25FL128SxxBxL0 [DX5146]	S25FL128SxxBxL1 [DX5146]
S25FL128SxxBxM0 [DX5157]	S25FL128SxxBxM1 [DX5157]
S25FL128SxxBxN0 [DX5146]	S25FL128SxxBxN1 [DX5146]
S25FL128SxxBxS0 [DX5157]	S25FL128SxxBxS1 [DX5157]
S25FL128SxxBxT0 [DX5146]	S25FL128SxxBxT1 [DX5146]
S25FL128SxxBxU0 [DX5157]	S25FL128SxxBxU1 [DX5157]
S25FL128SxxBxV0 [DX5146]	S25FL128SxxBxV1 [DX5146]
S25FL128SxxBxW0 [DX5157]	S25FL128SxxBxW1 [DX5157]

S25FL128SxxBxX0 [DX5146]
S25FL128SxxBxX1 [DX5146]
S25FL128SxxBxY0 [DX5157]
S25FL128SxxBxY1 [DX5157]
S25FL128SxxBxZ0 [DX5146]
S25FL128SxxBxZ1 [DX5146]
S25FL129P@BGA24(5*5 pin) [DX5157]
S25FL129P@BGA24(6*4 pin) [DX5146]
S25FL129P@SOIC16 [DX1072#1]
S25FL129P@WSON8 [DX4006#1]
S25FL132K@BGA24(5*5 pin) [DX5157]
S25FL132K@BGA24(6*4 pin) [DX5146]
S25FL132K@SOIC16 [DX1072#1]
S25FL132K@SOIC8(150 mil) [DX1045#1]
S25FL132K@SOIC8(200 mil) [DX1044#1]
S25FL132K@WSON8 [DX4005#1]
S25FL164K@BGA24(5*5 pin) [DX5157]
S25FL164K@BGA24(6*4 pin) [DX5146]
S25FL164K@SOIC16 [DX1072#1]
S25FL164K@SOIC8(150 mil) [DX1045#1]
S25FL164K@SOIC8(200 mil) [DX1044#1]
S25FL164K@WSON8 [DX4005#1]
S25FL204K@SOIC8[150 mil] [DX1045#1]
S25FL204K@SOIC8[208 mil] [DX1044#1]
S25FL208K@SOIC8[150 mil] [DX1045#1]
S25FL208K@SOIC8[208 mil] [DX1044#1]
S25FL216K@SOIC8[150 mil] [DX1045#1]
S25FL216K@SOIC8[208 mil] [DX1044#1]
S25FL256S(256byte)@BGA24[4*6] [DX5146]
S25FL256S(256byte)@BGA24[5*5] [DX5157]
S25FL256S(256byte)@SOIC16 [DX1033#1]
S25FL256S(256byte)@WSON8 [DX4006#1]
S25FL256S(512byte)@BGA24[4*6] [DX5146]
S25FL256S(512byte)@BGA24[5*5] [DX5157]
S25FL256S(512byte)@SOIC16 [DX1033#1]
S25FL256S(512byte)@WSON8 [DX4006#1]
S25FL256SAGBxx20 [DX5157]
S25FL256SAGBxx21 [DX5157]
S25FL256SAGBxx30 [DX5146]
S25FL256SAGBxx31 [DX5146]
S25FL256SAGBxx40 [DX5157]
S25FL256SAGBxx41 [DX5157]
S25FL256SAGBxx60 [DX5146]
S25FL256SAGBxx61 [DX5146]
S25FL256SAGBxx70 [DX5157]
S25FL256SAGBxx71 [DX5157]
S25FL256SAGBxx80 [DX5146]
S25FL256SAGBxx81 [DX5146]
S25FL256SAGBxxA0 [DX5157]
S25FL256SAGBxxA1 [DX5157]
S25FL256SAGBxxB0 [DX5146]
S25FL256SAGBxxB1 [DX5146]
S25FL256SAGBxxC0 [DX5157]
S25FL256SAGBxxC1 [DX5157]
S25FL256SAGBxxD0 [DX5146]
S25FL256SAGBxxD1 [DX5146]
S25FL256SAGBxxE0 [DX5157]
S25FL256SAGBxxE1 [DX5157]
S25FL256SAGBxxF0 [DX5146]
S25FL256SAGBxxF1 [DX5146]
S25FL256SAGMxx00 [DX1033#1]
S25FL256SAGMxx01 [DX1033#1]
S25FL256SAGMxx90 [DX1033#1]
S25FL256SAGMxx91 [DX1033#1]
S25FL256SAGMxxG0 [DX1033#1]
S25FL256SAGMxxG1 [DX1033#1]
S25FL256SAGMxxH0 [DX1033#1]
S25FL256SAGMxxH1 [DX1033#1]

S25FL256SAGMxxQ0 [DX1033#1]
S25FL256SAGMxxQ1 [DX1033#1]
S25FL256SAGMxxR0 [DX1033#1]
S25FL256SAGMxxR1 [DX1033#1]
S25FL256SAGNxx00 [DX4006#1]
S25FL256SAGNxx01 [DX4006#1]
S25FL256SAGNxx90 [DX4006#1]
S25FL256SAGNxx91 [DX4006#1]
S25FL256SDPBxx20 [DX5157]
S25FL256SDPBxx21 [DX5157]
S25FL256SDPBxx30 [DX5146]
S25FL256SDPBxx31 [DX5146]
S25FL256SDPBxx40 [DX5157]
S25FL256SDPBxx41 [DX5157]
S25FL256SDPBxx60 [DX5146]
S25FL256SDPBxx61 [DX5146]
S25FL256SDPBxx70 [DX5157]
S25FL256SDPBxx71 [DX5157]
S25FL256SDPBxx80 [DX5146]
S25FL256SDPBxx81 [DX5146]
S25FL256SDPBxxA0 [DX5157]
S25FL256SDPBxxA1 [DX5157]
S25FL256SDPBxxB0 [DX5146]
S25FL256SDPBxxB1 [DX5146]
S25FL256SDPBxxC0 [DX5157]
S25FL256SDPBxxC1 [DX5157]
S25FL256SDPBxxD0 [DX5146]
S25FL256SDPBxxD1 [DX5146]
S25FL256SDPBxxE0 [DX5157]
S25FL256SDPBxxE1 [DX5157]
S25FL256SDPBxxF0 [DX5146]
S25FL256SDPBxxF1 [DX5146]
S25FL256SDPMxx00 [DX1033#1]
S25FL256SDPMxx01 [DX1033#1]
S25FL256SDPMxx90 [DX1033#1]
S25FL256SDPMxx91 [DX1033#1]
S25FL256SDPMxxG0 [DX1033#1]
S25FL256SDPMxxG1 [DX1033#1]
S25FL256SDPMxxH0 [DX1033#1]
S25FL256SDPMxxH1 [DX1033#1]
S25FL256SDPMxxQ0 [DX1033#1]
S25FL256SDPMxxQ1 [DX1033#1]
S25FL256SDPMxxR0 [DX1033#1]
S25FL256SDPMxxR1 [DX1033#1]
S25FL256SDPNxx00 [DX4006#1]
S25FL256SDPNxx01 [DX4006#1]
S25FL256SDPNxx90 [DX4006#1]
S25FL256SDPNxx91 [DX4006#1]
S25FL256SxxBxK0 [DX5157]
S25FL256SxxBxK1 [DX5157]
S25FL256SxxBxL0 [DX5146]
S25FL256SxxBxL1 [DX5146]
S25FL256SxxBxM0 [DX5157]
S25FL256SxxBxM1 [DX5157]
S25FL256SxxBxN0 [DX5146]
S25FL256SxxBxN1 [DX5146]
S25FL256SxxBxS0 [DX5157]
S25FL256SxxBxS1 [DX5157]
S25FL256SxxBxT0 [DX5146]
S25FL256SxxBxT1 [DX5146]
S25FL256SxxBxU0 [DX5157]
S25FL256SxxBxU1 [DX5157]
S25FL256SxxBxV0 [DX5146]
S25FL256SxxBxV1 [DX5146]
S25FL256SxxBxW0 [DX5157]
S25FL256SxxBxW1 [DX5157]
S25FL256SxxBxX0 [DX5146]
S25FL256SxxBxX1 [DX5146]
S25FL256SxxBxY0 [DX5157]
S25FL256SxxBxY1 [DX5157]
S25FL256SxxBxZ0 [DX5146]
S25FL256SxxBxZ1 [DX5146]
S25FL512SAGBxx20 [DX5157]
S25FL512SAGBxx30 [DX5146]
S25FL512SAGBxx40 [DX5157]
S25FL512SAGBxx60 [DX5146]
S25FL512SAGBxx70 [DX5157]
S25FL512SAGBxx80 [DX5146]
S25FL512SAGBxxA0 [DX5157]
S25FL512SAGBxxB0 [DX5146]
S25FL512SAGBxxC0 [DX5157]
S25FL512SAGBxxD0 [DX5146]
S25FL512SAGBxxE0 [DX5157]
S25FL512SAGBxxF0 [DX5146]
S25FL512SAGBxxK1 [DX5157]
S25FL512SAGBxxL1 [DX5157]
S25FL512SAGBxxM1 [DX5157]
S25FL512SAGBxxN1 [DX5157]
S25FL512SAGBxxS1 [DX5157]
S25FL512SAGBxxT1 [DX5157]
S25FL512SAGBxxU1 [DX5157]
S25FL512SAGBxxV1 [DX5157]
S25FL512SAGBxxW1 [DX5157]
S25FL512SAGBxxX1 [DX5157]
S25FL512SAGBxxY1 [DX5157]
S25FL512SAGMxx00 [DX1033#1]

S25FL512SAGMxx90 [DX1033#1]
S25FL512SAGMxxG0 [DX1033#1]
S25FL512SAGMxxH0 [DX1033#1]
S25FL512SAGMxxQ0 [DX1033#1]
S25FL512SAGMxxR0 [DX1033#1]
S25FL512SDPBxx20 [DX5157]
S25FL512SDPBxx30 [DX5146]
S25FL512SDPBxx40 [DX5157]
S25FL512SDPBxx60 [DX5146]
S25FL512SDPBxx70 [DX5157]
S25FL512SDPBxx80 [DX5146]
S25FL512SDPBxxA0 [DX5157]
S25FL512SDPBxxB0 [DX5146]
S25FL512SDPBxxC0 [DX5157]
S25FL512SDPBxxD0 [DX5146]
S25FL512SDPBxxE0 [DX5157]
S25FL512SDPBxxF0 [DX5146]
S25FL512SDPBxxK1 [DX5157]
S25FL512SDPBxxL1 [DX5157]
S25FL512SDPBxxM1 [DX5157]
S25FL512SDPBxxN1 [DX5157]
S25FL512SDPBxxS1 [DX5157]
S25FL512SDPBxxT1 [DX5157]
S25FL512SDPBxxU1 [DX5157]
S25FL512SDPBxxV1 [DX5157]
S25FL512SDPBxxW1 [DX5157]
S25FL512SDPBxxX1 [DX5157]
S25FL512SDPBxxY1 [DX5157]
S25FL512SDPMxx00 [DX1033#1]
S25FL512SDPMxx90 [DX1033#1]
S25FL512SDPMxxG0 [DX1033#1]
S25FL512SDPMxxH0 [DX1033#1]
S25FL512SDPMxxQ0 [DX1033#1]
S25FL512SDPMxxR0 [DX1033#1]
S25FLK05D@SOIC8 [DX1045]
S25FLK05D@USON8 [DX4005]
S25FS128SAGBxx20 [DX5157]
S25FS128SAGBxx21 [DX5157]
S25FS128SAGBxx30 [DX5146]
S25FS128SAGBxx31 [DX5146]
S25FS128SAGBxx40 [DX5157]
S25FS128SAGBxx41 [DX5157]
S25FS128SAGBxx60 [DX5146]
S25FS128SAGBxx61 [DX5146]
S25FS128SAGBxx70 [DX5157]
S25FS128SAGBxx71 [DX5157]
S25FS128SAGBxx80 [DX5146]
S25FS128SAGBxx81 [DX5146]
S25FS128SAGBxxA0 [DX5157]
S25FS128SAGBxxA1 [DX5157]
S25FS128SAGBxxB0 [DX5146]
S25FS128SAGBxxB1 [DX5146]
S25FS128SAGBxxC0 [DX5157]
S25FS128SAGBxxC1 [DX5157]
S25FS128SAGBxxD0 [DX5146]
S25FS128SAGBxxD1 [DX5146]
S25FS128SAGBxxE0 [DX5157]
S25FS128SAGBxxE1 [DX5157]
S25FS128SAGBxxF0 [DX5146]
S25FS128SAGBxxF1 [DX5146]
S25FS128SAGMxx00 [DX1033#1]
S25FS128SAGMxx01 [DX1033#1]
S25FS128SAGMxx90 [DX1033#1]
S25FS128SAGMxx91 [DX1033#1]
S25FS128SAGMxxG0 [DX1033#1]
S25FS128SAGMxxG1 [DX1033#1]
S25FS128SAGMxxH0 [DX1033#1]
S25FS128SAGMxxH1 [DX1033#1]
S25FS128SAGMxxQ0 [DX1033#1]
S25FS128SAGMxxQ1 [DX1033#1]
S25FS128SAGMxxR0 [DX1033#1]
S25FS128SAGMxxR1 [DX1033#1]
S25FS128SAGNxx00 [DX4006#1]
S25FS128SAGNxx01 [DX4006#1]
S25FS128SAGNxx10 [DX1044#1]
S25FS128SAGNxx90 [DX4006#1]
S25FS128SAGNxx91 [DX4006#1]
S25FS256SAGBxx20 [DX5157]
S25FS256SAGBxx30 [DX5146]
S25FS256SAGMxx01 [DX1033#1]
S25FS256SAGNxx01 [DX4006#1]
S25FS512SAGBxx21 [DX5157]
S25FS512SAGMxx01 [DX1033#1]
S25FS512SAGNxx01 [DX4006#1]
S29AD016D11BFA01@FBGA48 [DX5043]
S29AD016D11BFA02@FBGA48 [DX5043]
S29AD016D11BFB01@FBGA48 [DX5043]
S29AD016D11BFB02@FBGA48 [DX5043]
S29AD016D11BFI01@FBGA48 [DX5043]
S29AD016D11BFI02@FBGA48 [DX5043]
S29AD016D11BFV01@FBGA48 [DX5043]
S29AD016D11BFV02@FBGA48 [DX5043]
S29AD016D11MFA01@PSOP44 [DX1014]
S29AD016D11MFA02@PSOP44 [DX1014]
S29AD016D11MFB01@PSOP44 [DX1014]
S29AD016D11MFB02@PSOP44 [DX1014]

S29AD016D11MFI01@PSOP44 [DX1014]
S29AD016D11MFI02@PSOP44 [DX1014]
S29AD016D11MFV01@PSOP44 [DX1014]
S29AD016D11MFV02@PSOP44 [DX1014]
S29AD016D11TFA01@TSOP48 [DX1004]
S29AD016D11TFA02@TSOP48 [DX1004]
S29AD016D11TFB01@TSOP48 [DX1004]
S29AD016D11TFB02@TSOP48 [DX1004]
S29AD016D11TFI01@TSOP48 [DX1004]
S29AD016D11TFI02@TSOP48 [DX1004]
S29AD016D11TFV01@TSOP48 [DX1004]
S29AD016D11TFV02@TSOP48 [DX1004]
S29AL002B55BAI01@FBGA48 [DX5043]
S29AL002B55BAI02@FBGA48 [DX5043]
S29AL002B55BFI01@FBGA48 [DX5043]
S29AL002B55BFI02@FBGA48 [DX5043]
S29AL002B55MAI01@PSOP44 [DX1014]
S29AL002B55MAI02@PSOP44 [DX1014]
S29AL002B55MFI01@PSOP44 [DX1014]
S29AL002B55MFI02@PSOP44 [DX1014]
S29AL002B55TAI01@TSOP48 [DX1004]
S29AL002B55TAI02@TSOP48 [DX1004]
S29AL002B55TFI01@TSOP48 [DX1004]
S29AL002B55TFI02@TSOP48 [DX1004]
S29AL004B55BAI01@FBGA48 [DX5043]
S29AL004B55BAI02@FBGA48 [DX5043]
S29AL004B55BFI01@FBGA48 [DX5043]
S29AL004B55BFI02@FBGA48 [DX5043]
S29AL004B55MAI01@PSOP44 [DX1014]
S29AL004B55MAI02@PSOP44 [DX1014]
S29AL004B55MFI01@PSOP44 [DX1014]
S29AL004B55MFI02@PSOP44 [DX1014]
S29AL004B55TAI01@TSOP48 [DX1004]
S29AL004B55TAI02@TSOP48 [DX1004]
S29AL004B55TFI01@TSOP48 [DX1004]
S29AL004B55TFI02@TSOP48 [DX1004]
S29AL004D55BAI01@FBGA48 [DX5043]
S29AL004D55BAI02@FBGA48 [DX5043]
S29AL004D55BANR1@FBGA48 [DX5043]
S29AL004D55BANR2@FBGA48 [DX5043]
S29AL004D55BFI01@FBGA48 [DX5043]
S29AL004D55BFI02@FBGA48 [DX5043]
S29AL004D55BFNR1@FBGA48 [DX5043]
S29AL004D55BFNR2@FBGA48 [DX5043]
S29AL004D55MAI01@PSOP44 [DX1014]
S29AL004D55MAI02@PSOP44 [DX1014]
S29AL004D55MANR1@PSOP44 [DX1014]
S29AL004D55MANR2@PSOP44 [DX1014]
S29AL004D55MFI01@PSOP44 [DX1014]
S29AL004D55MFI02@PSOP44 [DX1014]
S29AL004D55MFNR1@PSOP44 [DX1014]
S29AL004D55MFNR2@PSOP44 [DX1014]
S29AL004D55TAI01@TSOP48 [DX1004]
S29AL004D55TAI02@TSOP48 [DX1004]
S29AL004D55TANR1@TSOP48 [DX1004]
S29AL004D55TANR2@TSOP48 [DX1004]
S29AL004D55TFI01@TSOP48 [DX1004]
S29AL004D55TFI02@TSOP48 [DX1004]
S29AL004D55TFNR1@TSOP48 [DX1004]
S29AL004D55TFNR2@TSOP48 [DX1004]
S29AL004D70BAI01@FBGA48 [DX5043]
S29AL004D70BAI02@FBGA48 [DX5043]
S29AL004D70BAN01@FBGA48 [DX5043]
S29AL004D70BAN02@FBGA48 [DX5043]
S29AL004D70BFI01@FBGA48 [DX5043]
S29AL004D70BFI02@FBGA48 [DX5043]
S29AL004D70BFN01@FBGA48 [DX5043]
S29AL004D70BFN02@FBGA48 [DX5043]
S29AL004D70MAI01@PSOP44 [DX1014]
S29AL004D70MAI02@PSOP44 [DX1014]
S29AL004D70MAN01@PSOP44 [DX1014]
S29AL004D70MAN02@PSOP44 [DX1014]
S29AL004D70MFI01@PSOP44 [DX1014]
S29AL004D70MFI02@PSOP44 [DX1014]
S29AL004D70MFN01@PSOP44 [DX1014]
S29AL004D70MFN02@PSOP44 [DX1014]
S29AL004D70TAI01@TSOP48 [DX1004]
S29AL004D70TAI02@TSOP48 [DX1004]
S29AL004D70TAN01@TSOP48 [DX1004]
S29AL004D70TAN02@TSOP48 [DX1004]
S29AL004D70TFI01@TSOP48 [DX1004]
S29AL004D70TFI02@TSOP48 [DX1004]
S29AL004D70TFN01@TSOP48 [DX1004]
S29AL004D70TFN02@TSOP48 [DX1004]
S29AL004D90BAI01@FBGA48 [DX5043]
S29AL004D90BAI02@FBGA48 [DX5043]
S29AL004D90BAN01@FBGA48 [DX5043]
S29AL004D90BAN02@FBGA48 [DX5043]
S29AL004D90BFI01@FBGA48 [DX5043]
S29AL004D90BFI02@FBGA48 [DX5043]
S29AL004D90BFN01@FBGA48 [DX5043]
S29AL004D90BFN02@FBGA48 [DX5043]
S29AL004D90MAI01@PSOP44 [DX1014]
S29AL004D90MAI02@PSOP44 [DX1014]
S29AL004D90MAN01@PSOP44 [DX1014]
S29AL004D90MAN02@PSOP44 [DX1014]

S29AL004D90MFI01@PSOP44 [DX1014]
S29AL004D90MFI02@PSOP44 [DX1014]
S29AL004D90MFN01@PSOP44 [DX1014]
S29AL004D90MFN02@PSOP44 [DX1014]
S29AL004D90TAI01@TSOP48 [DX1004]
S29AL004D90TAI02@TSOP48 [DX1004]
S29AL004D90TAN01@TSOP48 [DX1004]
S29AL004D90TAN02@TSOP48 [DX1004]
S29AL004D90TFI01@TSOP48 [DX1004]
S29AL004D90TFI02@TSOP48 [DX1004]
S29AL004D90TFN01@TSOP48 [DX1004]
S29AL004D90TFN02@TSOP48 [DX1004]
S29AL008D55BAIR1@FBGA48 [DX5043]
S29AL008D55BAIR2@FBGA48 [DX5043]
S29AL008D55BFIR1@FBGA48 [DX5043]
S29AL008D55BFIR2@FBGA48 [DX5043]
S29AL008D55MAIR1@PSOP44 [DX1014]
S29AL008D55MAIR2@PSOP44 [DX1014]
S29AL008D55MFIR1@PSOP44 [DX1014]
S29AL008D55MFIR2@PSOP44 [DX1014]
S29AL008D55TAIR1@TSOP48 [DX1004]
S29AL008D55TAIR2@TSOP48 [DX1004]
S29AL008D55TFIR1@TSOP48 [DX1004]
S29AL008D55TFIR2@TSOP48 [DX1004]
S29AL008D60BAI01@FBGA48 [DX5043]
S29AL008D60BAI02@FBGA48 [DX5043]
S29AL008D60BAN01@FBGA48 [DX5043]
S29AL008D60BAN02@FBGA48 [DX5043]
S29AL008D60BFI01@FBGA48 [DX5043]
S29AL008D60BFI02@FBGA48 [DX5043]
S29AL008D60BFN01@FBGA48 [DX5043]
S29AL008D60BFN02@FBGA48 [DX5043]
S29AL008D60MAI01@PSOP44 [DX1014]
S29AL008D60MAI02@PSOP44 [DX1014]
S29AL008D60MAN01@PSOP44 [DX1014]
S29AL008D60MAN02@PSOP44 [DX1014]
S29AL008D60MFI01@PSOP44 [DX1014]
S29AL008D60MFI02@PSOP44 [DX1014]
S29AL008D60MFN01@PSOP44 [DX1014]
S29AL008D60MFN02@PSOP44 [DX1014]
S29AL008D60TAI01@TSOP48 [DX1004]
S29AL008D60TAI02@TSOP48 [DX1004]
S29AL008D60TAN01@TSOP48 [DX1004]
S29AL008D60TAN02@TSOP48 [DX1004]
S29AL008D60TFI01@TSOP48 [DX1004]
S29AL008D60TFI02@TSOP48 [DX1004]
S29AL008D60TFN01@TSOP48 [DX1004]
S29AL008D60TFN02@TSOP48 [DX1004]
S29AL008D70BAI01@FBGA48 [DX5043]
S29AL008D70BAI02@FBGA48 [DX5043]
S29AL008D70BAN01@FBGA48 [DX5043]
S29AL008D70BAN02@FBGA48 [DX5043]
S29AL008D70BFI01@FBGA48 [DX5043]
S29AL008D70BFI02@FBGA48 [DX5043]
S29AL008D70BFN01@FBGA48 [DX5043]
S29AL008D70BFN02@FBGA48 [DX5043]
S29AL008D70MAI01@PSOP44 [DX1014]
S29AL008D70MAI02@PSOP44 [DX1014]
S29AL008D70MAN01@PSOP44 [DX1014]
S29AL008D70MAN02@PSOP44 [DX1014]
S29AL008D70MFI01@PSOP44 [DX1014]
S29AL008D70MFI02@PSOP44 [DX1014]
S29AL008D70MFN01@PSOP44 [DX1014]
S29AL008D70MFN02@PSOP44 [DX1014]
S29AL008D70TAI01@TSOP48 [DX1004]
S29AL008D70TAI02@TSOP48 [DX1004]
S29AL008D70TAN01@TSOP48 [DX1004]
S29AL008D70TAN02@TSOP48 [DX1004]
S29AL008D70TFI01@TSOP48 [DX1004]
S29AL008D70TFI02@TSOP48 [DX1004]
S29AL008D70TFN01@TSOP48 [DX1004]
S29AL008D70TFN02@TSOP48 [DX1004]
S29AL008D90BAI01@FBGA48 [DX5043]
S29AL008D90BAI02@FBGA48 [DX5043]
S29AL008D90BAN01@FBGA48 [DX5043]
S29AL008D90BAN02@FBGA48 [DX5043]
S29AL008D90BFI01@FBGA48 [DX5043]
S29AL008D90BFI02@FBGA48 [DX5043]
S29AL008D90BFN01@FBGA48 [DX5043]
S29AL008D90BFN02@FBGA48 [DX5043]
S29AL008D90MAI01@PSOP44 [DX1014]
S29AL008D90MAI02@PSOP44 [DX1014]
S29AL008D90MAN01@PSOP44 [DX1014]
S29AL008D90MAN02@PSOP44 [DX1014]
S29AL008D90MFI01@PSOP44 [DX1014]
S29AL008D90MFI02@PSOP44 [DX1014]
S29AL008D90MFN01@PSOP44 [DX1014]
S29AL008D90MFN02@PSOP44 [DX1014]
S29AL008D90TAI01@TSOP48 [DX1004]
S29AL008D90TAI02@TSOP48 [DX1004]
S29AL008D90TAN01@TSOP48 [DX1004]
S29AL008D90TAN02@TSOP48 [DX1004]
S29AL008D90TFI01@TSOP48 [DX1004]
S29AL008D90TFI02@TSOP48 [DX1004]
S29AL008D90TFN01@TSOP48 [DX1004]
S29AL008D90TFN02@TSOP48 [DX1004]

S29AL008J55BFIR1@FBGA48 [DX5043]
S29AL008J55BFIR2@FBGA48 [DX5043]
S29AL008J55BFNR1@FBGA48 [DX5043]
S29AL008J55BFNR2@FBGA48 [DX5043]
S29AL008J55SFIR1@SSOP56 [DX1029]
S29AL008J55SFIR2@SSOP56 [DX1029]
S29AL008J55SFNR1@SSOP56 [DX1029]
S29AL008J55SFNR2@SSOP56 [DX1029]
S29AL008J55TFIR1@TSOP48 [DX1043]
S29AL008J55TFIR2@TSOP48 [DX1043]
S29AL008J55TFNR1@TSOP48 [DX1043]
S29AL008J55TFNR2@TSOP48 [DX1043]
S29AL008J70BFI01@FBGA48 [DX5043]
S29AL008J70BFI02@FBGA48 [DX5043]
S29AL008J70BFI03@FBGA48 [DX5043]
S29AL008J70BFI04@FBGA48 [DX5043]
S29AL008J70BFN01@FBGA48 [DX5043]
S29AL008J70BFN02@FBGA48 [DX5043]
S29AL008J70SFI01@SSOP56 [DX1029]
S29AL008J70SFI02@SSOP56 [DX1029]
S29AL008J70SFN01@SSOP56 [DX1029]
S29AL008J70SFN02@SSOP56 [DX1029]
S29AL008J70TFI01@TSOP48 [DX1043]
S29AL008J70TFI02@TSOP48 [DX1043]
S29AL008J70TFI03@TSOP48 [DX1043]
S29AL008J70TFI04@TSOP48 [DX1043]
S29AL008J70TFN01@TSOP48 [DX1043]
S29AL008J70TFN02@TSOP48 [DX1043]
S29AL016D70BAI01@FBGA48 [DX5043]
S29AL016D70BAI02@FBGA48 [DX5043]
S29AL016D70BAN01@FBGA48 [DX5043]
S29AL016D70BAN02@FBGA48 [DX5043]
S29AL016D70BFI01@FBGA48 [DX5043]
S29AL016D70BFI02@FBGA48 [DX5043]
S29AL016D70BFN01@FBGA48 [DX5043]
S29AL016D70BFN02@FBGA48 [DX5043]
S29AL016D70MAI01@PSOP44 [DX1014]
S29AL016D70MAI02@PSOP44 [DX1014]
S29AL016D70MAN01@PSOP44 [DX1014]
S29AL016D70MAN02@PSOP44 [DX1014]
S29AL016D70MFI01@PSOP44 [DX1014]
S29AL016D70MFI02@PSOP44 [DX1014]
S29AL016D70MFN01@PSOP44 [DX1014]
S29AL016D70MFN02@PSOP44 [DX1014]
S29AL016D70TAI01@TSOP48 [DX1004]
S29AL016D70TAI02@TSOP48 [DX1004]
S29AL016D70TAN01@TSOP48 [DX1004]
S29AL016D70TAN02@TSOP48 [DX1004]
S29AL016D70TFI01@TSOP48 [DX1004]
S29AL016D70TFI02@TSOP48 [DX1004]
S29AL016D70TFN01@TSOP48 [DX1004]
S29AL016D70TFN02@TSOP48 [DX1004]
S29AL016D90BAI01@FBGA48 [DX5043]
S29AL016D90BAI02@FBGA48 [DX5043]
S29AL016D90BAN01@FBGA48 [DX5043]
S29AL016D90BAN02@FBGA48 [DX5043]
S29AL016D90BFI01@FBGA48 [DX5043]
S29AL016D90BFI02@FBGA48 [DX5043]
S29AL016D90BFN01@FBGA48 [DX5043]
S29AL016D90BFN02@FBGA48 [DX5043]
S29AL016D90MAI01@PSOP44 [DX1014]
S29AL016D90MAI02@PSOP44 [DX1014]
S29AL016D90MAN01@PSOP44 [DX1014]
S29AL016D90MAN02@PSOP44 [DX1014]
S29AL016D90MFI01@PSOP44 [DX1014]
S29AL016D90MFI02@PSOP44 [DX1014]
S29AL016D90MFN01@PSOP44 [DX1014]
S29AL016D90MFN02@PSOP44 [DX1014]
S29AL016D90TAI01@TSOP48 [DX1004]
S29AL016D90TAI02@TSOP48 [DX1004]
S29AL016D90TAN01@TSOP48 [DX1004]
S29AL016D90TAN02@TSOP48 [DX1004]
S29AL016D90TFI01@TSOP48 [DX1004]
S29AL016D90TFI02@TSOP48 [DX1004]
S29AL016D90TFN01@TSOP48 [DX1004]
S29AL016D90TFN02@TSOP48 [DX1004]
S29AL016J55BFIR1@FBGA48 [DX5043]
S29AL016J55BFIR2@FBGA48 [DX5043]
S29AL016J55BFNR1@FBGA48 [DX5043]
S29AL016J55BFNR2@FBGA48 [DX5043]
S29AL016J55FFIR1@FBGA64 [DX5103]
S29AL016J55FFIR2@FBGA64 [DX5103]
S29AL016J55FFNR1@FBGA64 [DX5103]
S29AL016J55FFNR2@FBGA64 [DX5103]
S29AL016J55TFIR1@TSOP48 [DX1043]
S29AL016J55TFIR2@TSOP48 [DX1043]
S29AL016J55TFNR1@TSOP48 [DX1043]
S29AL016J55TFNR2@TSOP48 [DX1043]
S29AL016J70BFI01@FBGA48 [DX5043]
S29AL016J70BFI02@FBGA48 [DX5043]
S29AL016J70BFI03@FBGA48 [DX5043]
S29AL016J70BFI04@FBGA48 [DX5043]
S29AL016J70BFN01@FBGA48 [DX5043]
S29AL016J70BFN02@FBGA48 [DX5043]
S29AL016J70FFI01@FBGA64 [DX5103]
S29AL016J70FFI02@FBGA64 [DX5103]

S29AL016J70FFN01@FBGA64 [DX5103]　　S29AL016J70FFN02@FBGA64 [DX5103]
S29AL016J70SFI01@SSOP56 [DX1029]　　S29AL016J70SFI02@SSOP56 [DX1029]
S29AL016J70SFN01@SSOP56 [DX1029]　　S29AL016J70SFN02@SSOP56 [DX1029]
S29AL016J70TFI01@TSOP48 [DX1043]　　S29AL016J70TFI02@TSOP48 [DX1043]
S29AL016J70TFI03@TSOP48 [DX1043]　　S29AL016J70TFI04@TSOP48 [DX1043]
S29AL016J70TFN01@TSOP48 [DX1043]　　S29AL016J70TFN02@TSOP48 [DX1043]
S29AL016M10BAI01@FBGA48 [DX5002]　　S29AL016M10BAI02@FBGA48 [DX5002]
S29AL016M10BAIR1@FBGA48 [DX5002]　　S29AL016M10BAIR2@FBGA48 [DX5002]
S29AL016M10BFI01@FBGA48 [DX5002]　　S29AL016M10BFI02@FBGA48 [DX5002]
S29AL016M10BFIR1@FBGA48 [DX5002]　　S29AL016M10BFIR2@FBGA48 [DX5002]
S29AL016M10FAI01@FBGA64 [DX5074]　　S29AL016M10FAI02@FBGA64 [DX5074]
S29AL016M10FAIR1@FBGA64 [DX5074]　　S29AL016M10FAIR2@FBGA64 [DX5074]
S29AL016M10FFI01@FBGA64 [DX5074]　　S29AL016M10FFI02@FBGA64 [DX5074]
S29AL016M10FFIR1@FBGA64 [DX5074]　　S29AL016M10FFIR2@FBGA64 [DX5074]
S29AL016M10TAI01@TSOP48 [DX1004]　　S29AL016M10TAI02@TSOP48 [DX1004]
S29AL016M10TAIR1@TSOP48 [DX1004]　　S29AL016M10TAIR2@TSOP48 [DX1004]
S29AL016M10TFI01@TSOP48 [DX1004]　　S29AL016M10TFI02@TSOP48 [DX1004]
S29AL016M10TFIR1@TSOP48 [DX1004]　　S29AL016M10TFIR2@TSOP48 [DX1004]
S29AL016M90BAI01@FBGA48 [DX5002]　　S29AL016M90BAI02@FBGA48 [DX5002]
S29AL016M90BAIR1@FBGA48 [DX5002]　　S29AL016M90BAIR2@FBGA48 [DX5002]
S29AL016M90BFI01@FBGA48 [DX5002]　　S29AL016M90BFI02@FBGA48 [DX5002]
S29AL016M90BFIR1@FBGA48 [DX5002]　　S29AL016M90BFIR2@FBGA48 [DX5002]
S29AL016M90FAI01@FBGA64 [DX5074]　　S29AL016M90FAI02@FBGA64 [DX5074]
S29AL016M90FAIR1@FBGA64 [DX5074]　　S29AL016M90FAIR2@FBGA64 [DX5074]
S29AL016M90FFI01@FBGA64 [DX5074]　　S29AL016M90FFI02@FBGA64 [DX5074]
S29AL016M90FFIR1@FBGA64 [DX5074]　　S29AL016M90FFIR2@FBGA64 [DX5074]
S29AL016M90TAI01@TSOP48 [DX1004]　　S29AL016M90TAI02@TSOP48 [DX1004]
S29AL016M90TAIR1@TSOP48 [DX1004]　　S29AL016M90TAIR2@TSOP48 [DX1004]
S29AL016M90TFI01@TSOP48 [DX1004]　　S29AL016M90TFI02@TSOP48 [DX1004]
S29AL016M90TFIR1@TSOP48 [DX1004]　　S29AL016M90TFIR2@TSOP48 [DX1004]
S29AL032D70BAI00@FBGA48 [DX5083]　　S29AL032D70BAI03@FBGA48 [DX5083]
S29AL032D70BAI04@FBGA48 [DX5083]　　S29AL032D70BFI00@FBGA48 [DX5083]
S29AL032D70BFI03(new)@FBGA48 [DX5083]
S29AL032D70BFI03@FBGA48 [DX5083]
S29AL032D70BFI04(new)@FBGA48 [DX5083]
S29AL032D70BFI04@FBGA48 [DX5083]　　S29AL032D70TAI00@TSOP40 [DX1006]
S29AL032D70TAI03@TSOP48 [DX1004]　　S29AL032D70TAI04@TSOP48 [DX1004]
S29AL032D70TFI00@TSOP40 [DX1006]　　S29AL032D70TFI03@TSOP48 [DX1004]
S29AL032D70TFI04@TSOP48 [DX1004]　　S29AL032D90BAI00@FBGA48 [DX5083]
S29AL032D90BAI03@FBGA48 [DX5083]　　S29AL032D90BAI04@FBGA48 [DX5083]
S29AL032D90BAN00@FBGA48 [DX5083]　　S29AL032D90BAN03@FBGA48 [DX5083]
S29AL032D90BAN04@FBGA48 [DX5083]　　S29AL032D90BFI00@FBGA48 [DX5083]
S29AL032D90BFI03@FBGA48 [DX5083]　　S29AL032D90BFI04@FBGA48 [DX5083]
S29AL032D90BFN00@FBGA48 [DX5083]　　S29AL032D90BFN03@FBGA48 [DX5083]
S29AL032D90BFN04@FBGA48 [DX5083]　　S29AL032D90TAI00@TSOP40 [DX1006]
S29AL032D90TAI03@TSOP48 [DX1004]　　S29AL032D90TAI04@TSOP48 [DX1004]
S29AL032D90TAN00@TSOP40 [DX1006]　　S29AL032D90TAN03@TSOP48 [DX1004]
S29AL032D90TAN04@TSOP48 [DX1004]　　S29AL032D90TFI00@TSOP40 [DX1006]

S29AL032D90TFI03@TSOP48 [DX1004]
S29AL032D90TFI04@TSOP48 [DX1004]
S29AL032D90TFN00@TSOP40 [DX1006]
S29AL032D90TFN03@TSOP48 [DX1004]
S29AL032D90TFN04@TSOP48 [DX1004]
S29AS008J70BFI01@FBGA48 [DX5043]
S29AS008J70BFI02@FBGA48 [DX5043]
S29AS008J70BFI03@FBGA48 [DX5043]
S29AS008J70BFI04@FBGA48 [DX5043]
S29AS008J70TFI01@TSOP48 [DX1004]
S29AS008J70TFI02@TSOP48 [DX1004]
S29AS008J70TFI03@TSOP48 [DX1004]
S29AS008J70TFI04@TSOP48 [DX1004]
S29AS016J70BFI01@FBGA48 [DX5043]
S29AS016J70BFI02@FBGA48 [DX5043]
S29AS016J70BFI03@FBGA48 [DX5043]
S29AS016J70BFI04@FBGA48 [DX5043]
S29AS016J70BFV03@FBGA48 [DX5043]
S29AS016J70BFV04@FBGA48 [DX5043]
S29AS016J70BHI01@FBGA48 [DX5043]
S29AS016J70BHI02@FBGA48 [DX5043]
S29AS016J70BHI03@FBGA48 [DX5043]
S29AS016J70BHI04@FBGA48 [DX5043]
S29AS016J70BHIF3@WFBGA48 [DX5037]
S29AS016J70BHIF4@WFBGA48 [DX5037]
S29AS016J70BHV03@FBGA48 [DX5043]
S29AS016J70BHV04@FBGA48 [DX5043]
S29AS016J70TFI01@TSOP48 [DX1004]
S29AS016J70TFI02@TSOP48 [DX1004]
S29AS016J70TFI03@TSOP48 [DX1004]
S29AS016J70TFI04@TSOP48 [DX1004]
S29AS016J90BFV03@FBGA48 [DX5043]
S29AS016J90BFV04@FBGA48 [DX5043]
S29AS016J90BHV03@FBGA48 [DX5043]
S29AS016J90BHV04@FBGA48 [DX5043]
S29CD016J0JFAI00@FBGA80 [DX5258]
S29CD016J0JFAI01@FBGA80 [DX5258]
S29CD016J0JFAI02@FBGA80 [DX5258]
S29CD016J0JFAI03@FBGA80 [DX5258]
S29CD016J0JFAI10@FBGA80 [DX5258]
S29CD016J0JFAI11@FBGA80 [DX5258]
S29CD016J0JFAI12@FBGA80 [DX5258]
S29CD016J0JFAI13@FBGA80 [DX5258]
S29CD016J0JFAM00@FBGA80 [DX5258]
S29CD016J0JFAM01@FBGA80 [DX5258]
S29CD016J0JFAM02@FBGA80 [DX5258]
S29CD016J0JFAM03@FBGA80 [DX5258]
S29CD016J0JFAM10@FBGA80 [DX5258]
S29CD016J0JFAM11@FBGA80 [DX5258]
S29CD016J0JFAM12@FBGA80 [DX5258]
S29CD016J0JFAM13@FBGA80 [DX5258]
S29CD016J0JFFI00@FBGA80 [DX5258]
S29CD016J0JFFI01@FBGA80 [DX5258]
S29CD016J0JFFI02@FBGA80 [DX5258]
S29CD016J0JFFI03@FBGA80 [DX5258]
S29CD016J0JFFI10@FBGA80 [DX5258]
S29CD016J0JFFI11@FBGA80 [DX5258]
S29CD016J0JFFI12@FBGA80 [DX5258]
S29CD016J0JFFI13@FBGA80 [DX5258]
S29CD016J0JFFM00@FBGA80 [DX5258]
S29CD016J0JFFM01@FBGA80 [DX5258]
S29CD016J0JFFM02@FBGA80 [DX5258]
S29CD016J0JFFM03@FBGA80 [DX5258]
S29CD016J0JFFM10@FBGA80 [DX5258]
S29CD016J0JFFM11@FBGA80 [DX5258]
S29CD016J0JFFM12@FBGA80 [DX5258]
S29CD016J0JFFM13@FBGA80 [DX5258]
S29CD016J0JQAI00@PQFP80 [DX3020]
S29CD016J0JQAI01@PQFP80 [DX3020]
S29CD016J0JQAI02@PQFP80 [DX3020]
S29CD016J0JQAI03@PQFP80 [DX3020]
S29CD016J0JQAI10@PQFP80 [DX3020]
S29CD016J0JQAI11@PQFP80 [DX3020]
S29CD016J0JQAI12@PQFP80 [DX3020]
S29CD016J0JQAI13@PQFP80 [DX3020]
S29CD016J0JQAM00@PQFP80 [DX3020]
S29CD016J0JQAM01@PQFP80 [DX3020]
S29CD016J0JQAM02@PQFP80 [DX3020]
S29CD016J0JQAM03@PQFP80 [DX3020]
S29CD016J0JQAM10@PQFP80 [DX3020]
S29CD016J0JQAM11@PQFP80 [DX3020]
S29CD016J0JQAM12@PQFP80 [DX3020]
S29CD016J0JQAM13@PQFP80 [DX3020]
S29CD016J0JQFI00@PQFP80 [DX3020]
S29CD016J0JQFI01@PQFP80 [DX3020]
S29CD016J0JQFI02@PQFP80 [DX3020]
S29CD016J0JQFI03@PQFP80 [DX3020]
S29CD016J0JQFI10@PQFP80 [DX3020]
S29CD016J0JQFI11@PQFP80 [DX3020]
S29CD016J0JQFI12@PQFP80 [DX3020]
S29CD016J0JQFI13@PQFP80 [DX3020]
S29CD016J0JQFM00@PQFP80 [DX3020]
S29CD016J0JQFM01@PQFP80 [DX3020]

S29CD016J0JQFM02@PQFP80 [DX3020]
S29CD016J0JQFM03@PQFP80 [DX3020]
S29CD016J0JQFM10@PQFP80 [DX3020]
S29CD016J0JQFM11@PQFP80 [DX3020]
S29CD016J0JQFM12@PQFP80 [DX3020]
S29CD016J0JQFM13@PQFP80 [DX3020]
S29CD016J0MFAI00@FBGA80 [DX5258]
S29CD016J0MFAI01@FBGA80 [DX5258]
S29CD016J0MFAI02@FBGA80 [DX5258]
S29CD016J0MFAI03@FBGA80 [DX5258]
S29CD016J0MFAI10@FBGA80 [DX5258]
S29CD016J0MFAI11@FBGA80 [DX5258]
S29CD016J0MFAI12@FBGA80 [DX5258]
S29CD016J0MFAI13@FBGA80 [DX5258]
S29CD016J0MFAM00@FBGA80 [DX5258]
S29CD016J0MFAM01@FBGA80 [DX5258]
S29CD016J0MFAM02@FBGA80 [DX5258]
S29CD016J0MFAM03@FBGA80 [DX5258]
S29CD016J0MFAM10@FBGA80 [DX5258]
S29CD016J0MFAM11@FBGA80 [DX5258]
S29CD016J0MFAM12@FBGA80 [DX5258]
S29CD016J0MFAM13@FBGA80 [DX5258]
S29CD016J0MFFI00@FBGA80 [DX5258]
S29CD016J0MFFI01@FBGA80 [DX5258]
S29CD016J0MFFI02@FBGA80 [DX5258]
S29CD016J0MFFI03@FBGA80 [DX5258]
S29CD016J0MFFI10@FBGA80 [DX5258]
S29CD016J0MFFI11@FBGA80 [DX5258]
S29CD016J0MFFI12@FBGA80 [DX5258]
S29CD016J0MFFI13@FBGA80 [DX5258]
S29CD016J0MFFM00@FBGA80 [DX5258]
S29CD016J0MFFM01@FBGA80 [DX5258]
S29CD016J0MFFM02@FBGA80 [DX5258]
S29CD016J0MFFM03@FBGA80 [DX5258]
S29CD016J0MFFM10@FBGA80 [DX5258]
S29CD016J0MFFM11@FBGA80 [DX5258]
S29CD016J0MFFM12@FBGA80 [DX5258]
S29CD016J0MFFM13@FBGA80 [DX5258]
S29CD016J0MQAI00@PQFP80 [DX3020]
S29CD016J0MQAI01@PQFP80 [DX3020]
S29CD016J0MQAI02@PQFP80 [DX3020]
S29CD016J0MQAI03@PQFP80 [DX3020]
S29CD016J0MQAI10@PQFP80 [DX3020]
S29CD016J0MQAI11@PQFP80 [DX3020]
S29CD016J0MQAI12@PQFP80 [DX3020]
S29CD016J0MQAI13@PQFP80 [DX3020]
S29CD016J0MQAM00@PQFP80 [DX3020]
S29CD016J0MQAM01@PQFP80 [DX3020]
S29CD016J0MQAM02@PQFP80 [DX3020]
S29CD016J0MQAM03@PQFP80 [DX3020]
S29CD016J0MQAM10@PQFP80 [DX3020]
S29CD016J0MQAM11@PQFP80 [DX3020]
S29CD016J0MQAM12@PQFP80 [DX3020]
S29CD016J0MQAM13@PQFP80 [DX3020]
S29CD016J0MQFI00@PQFP80 [DX3020]
S29CD016J0MQFI01@PQFP80 [DX3020]
S29CD016J0MQFI02@PQFP80 [DX3020]
S29CD016J0MQFI03@PQFP80 [DX3020]
S29CD016J0MQFI10@PQFP80 [DX3020]
S29CD016J0MQFI11@PQFP80 [DX3020]
S29CD016J0MQFI12@PQFP80 [DX3020]
S29CD016J0MQFI13@PQFP80 [DX3020]
S29CD016J0MQFM00@PQFP80 [DX3020]
S29CD016J0MQFM01@PQFP80 [DX3020]
S29CD016J0MQFM02@PQFP80 [DX3020]
S29CD016J0MQFM03@PQFP80 [DX3020]
S29CD016J0MQFM10@PQFP80 [DX3020]
S29CD016J0MQFM11@PQFP80 [DX3020]
S29CD016J0MQFM12@PQFP80 [DX3020]
S29CD016J0MQFM13@PQFP80 [DX3020]
S29CD016J0PFAI00@FBGA80 [DX5258]
S29CD016J0PFAI01@FBGA80 [DX5258]
S29CD016J0PFAI02@FBGA80 [DX5258]
S29CD016J0PFAI03@FBGA80 [DX5258]
S29CD016J0PFAI10@FBGA80 [DX5258]
S29CD016J0PFAI11@FBGA80 [DX5258]
S29CD016J0PFAI12@FBGA80 [DX5258]
S29CD016J0PFAI13@FBGA80 [DX5258]
S29CD016J0PFAM00@FBGA80 [DX5258]
S29CD016J0PFAM01@FBGA80 [DX5258]
S29CD016J0PFAM02@FBGA80 [DX5258]
S29CD016J0PFAM03@FBGA80 [DX5258]
S29CD016J0PFAM10@FBGA80 [DX5258]
S29CD016J0PFAM11@FBGA80 [DX5258]
S29CD016J0PFAM12@FBGA80 [DX5258]
S29CD016J0PFAM13@FBGA80 [DX5258]
S29CD016J0PFFI00@FBGA80 [DX5258]
S29CD016J0PFFI01@FBGA80 [DX5258]
S29CD016J0PFFI02@FBGA80 [DX5258]
S29CD016J0PFFI03@FBGA80 [DX5258]
S29CD016J0PFFI10@FBGA80 [DX5258]
S29CD016J0PFFI11@FBGA80 [DX5258]
S29CD016J0PFFI12@FBGA80 [DX5258]
S29CD016J0PFFI13@FBGA80 [DX5258]
S29CD016J0PFFM00@FBGA80 [DX5258]
S29CD016J0PFFM01@FBGA80 [DX5258]

S29CD016J0PFFM02@FBGA80 [DX5258]
S29CD016J0PFFM03@FBGA80 [DX5258]
S29CD016J0PFFM10@FBGA80 [DX5258]
S29CD016J0PFFM11@FBGA80 [DX5258]
S29CD016J0PFFM12@FBGA80 [DX5258]
S29CD016J0PFFM13@FBGA80 [DX5258]
S29CD016J0PQAI00@PQFP80 [DX3020]
S29CD016J0PQAI01@PQFP80 [DX3020]
S29CD016J0PQAI02@PQFP80 [DX3020]
S29CD016J0PQAI03@PQFP80 [DX3020]
S29CD016J0PQAI10@PQFP80 [DX3020]
S29CD016J0PQAI11@PQFP80 [DX3020]
S29CD016J0PQAI12@PQFP80 [DX3020]
S29CD016J0PQAI13@PQFP80 [DX3020]
S29CD016J0PQAM00@PQFP80 [DX3020]
S29CD016J0PQAM01@PQFP80 [DX3020]
S29CD016J0PQAM02@PQFP80 [DX3020]
S29CD016J0PQAM03@PQFP80 [DX3020]
S29CD016J0PQAM10@PQFP80 [DX3020]
S29CD016J0PQAM11@PQFP80 [DX3020]
S29CD016J0PQAM12@PQFP80 [DX3020]
S29CD016J0PQAM13@PQFP80 [DX3020]
S29CD016J0PQFI00@PQFP80 [DX3020]
S29CD016J0PQFI01@PQFP80 [DX3020]
S29CD016J0PQFI02@PQFP80 [DX3020]
S29CD016J0PQFI03@PQFP80 [DX3020]
S29CD016J0PQFI10@PQFP80 [DX3020]
S29CD016J0PQFI11@PQFP80 [DX3020]
S29CD016J0PQFI12@PQFP80 [DX3020]
S29CD016J0PQFI13@PQFP80 [DX3020]
S29CD016J0PQFM00@PQFP80 [DX3020]
S29CD016J0PQFM01@PQFP80 [DX3020]
S29CD016J0PQFM02@PQFP80 [DX3020]
S29CD016J0PQFM03@PQFP80 [DX3020]
S29CD016J0PQFM10@PQFP80 [DX3020]
S29CD016J0PQFM11@PQFP80 [DX3020]
S29CD016J0PQFM12@PQFP80 [DX3020]
S29CD016J0PQFM13@PQFP80 [DX3020]
S29CD016J1JFAI00@FBGA80 [DX5258]
S29CD016J1JFAI01@FBGA80 [DX5258]
S29CD016J1JFAI02@FBGA80 [DX5258]
S29CD016J1JFAI03@FBGA80 [DX5258]
S29CD016J1JFAI10@FBGA80 [DX5258]
S29CD016J1JFAI11@FBGA80 [DX5258]
S29CD016J1JFAI12@FBGA80 [DX5258]
S29CD016J1JFAI13@FBGA80 [DX5258]
S29CD016J1JFAM00@FBGA80 [DX5258]
S29CD016J1JFAM01@FBGA80 [DX5258]
S29CD016J1JFAM02@FBGA80 [DX5258]
S29CD016J1JFAM03@FBGA80 [DX5258]
S29CD016J1JFAM10@FBGA80 [DX5258]
S29CD016J1JFAM11@FBGA80 [DX5258]
S29CD016J1JFAM12@FBGA80 [DX5258]
S29CD016J1JFAM13@FBGA80 [DX5258]
S29CD016J1JFFI00@FBGA80 [DX5258]
S29CD016J1JFFI01@FBGA80 [DX5258]
S29CD016J1JFFI02@FBGA80 [DX5258]
S29CD016J1JFFI03@FBGA80 [DX5258]
S29CD016J1JFFI10@FBGA80 [DX5258]
S29CD016J1JFFI11@FBGA80 [DX5258]
S29CD016J1JFFI12@FBGA80 [DX5258]
S29CD016J1JFFI13@FBGA80 [DX5258]
S29CD016J1JFFM00@FBGA80 [DX5258]
S29CD016J1JFFM01@FBGA80 [DX5258]
S29CD016J1JFFM02@FBGA80 [DX5258]
S29CD016J1JFFM03@FBGA80 [DX5258]
S29CD016J1JFFM10@FBGA80 [DX5258]
S29CD016J1JFFM11@FBGA80 [DX5258]
S29CD016J1JFFM12@FBGA80 [DX5258]
S29CD016J1JFFM13@FBGA80 [DX5258]
S29CD016J1JQAI00@PQFP80 [DX3020]
S29CD016J1JQAI01@PQFP80 [DX3020]
S29CD016J1JQAI02@PQFP80 [DX3020]
S29CD016J1JQAI03@PQFP80 [DX3020]
S29CD016J1JQAI10@PQFP80 [DX3020]
S29CD016J1JQAI11@PQFP80 [DX3020]
S29CD016J1JQAI12@PQFP80 [DX3020]
S29CD016J1JQAI13@PQFP80 [DX3020]
S29CD016J1JQAM00@PQFP80 [DX3020]
S29CD016J1JQAM01@PQFP80 [DX3020]
S29CD016J1JQAM02@PQFP80 [DX3020]
S29CD016J1JQAM03@PQFP80 [DX3020]
S29CD016J1JQAM10@PQFP80 [DX3020]
S29CD016J1JQAM11@PQFP80 [DX3020]
S29CD016J1JQAM12@PQFP80 [DX3020]
S29CD016J1JQAM13@PQFP80 [DX3020]
S29CD016J1JQFI00@PQFP80 [DX3020]
S29CD016J1JQFI01@PQFP80 [DX3020]
S29CD016J1JQFI02@PQFP80 [DX3020]
S29CD016J1JQFI03@PQFP80 [DX3020]
S29CD016J1JQFI10@PQFP80 [DX3020]
S29CD016J1JQFI11@PQFP80 [DX3020]
S29CD016J1JQFI12@PQFP80 [DX3020]
S29CD016J1JQFI13@PQFP80 [DX3020]
S29CD016J1JQFM00@PQFP80 [DX3020]
S29CD016J1JQFM01@PQFP80 [DX3020]

S29CD016J1JQFM02@PQFP80 [DX3020]
S29CD016J1JQFM03@PQFP80 [DX3020]
S29CD016J1JQFM10@PQFP80 [DX3020]
S29CD016J1JQFM11@PQFP80 [DX3020]
S29CD016J1JQFM12@PQFP80 [DX3020]
S29CD016J1JQFM13@PQFP80 [DX3020]
S29CD032J0JFAI00@FBGA80 [DX5258]
S29CD032J0JFAI01@FBGA80 [DX5258]
S29CD032J0JFAI02@FBGA80 [DX5258]
S29CD032J0JFAI03@FBGA80 [DX5258]
S29CD032J0JFAM00@FBGA80 [DX5258]
S29CD032J0JFAM01@FBGA80 [DX5258]
S29CD032J0JFAM02@FBGA80 [DX5258]
S29CD032J0JFAM03@FBGA80 [DX5258]
S29CD032J0JFFI00@FBGA80 [DX5258]
S29CD032J0JFFI01@FBGA80 [DX5258]
S29CD032J0JFFI02@FBGA80 [DX5258]
S29CD032J0JFFI03@FBGA80 [DX5258]
S29CD032J0JFFM00@FBGA80 [DX5258]
S29CD032J0JFFM01@FBGA80 [DX5258]
S29CD032J0JFFM02@FBGA80 [DX5258]
S29CD032J0JFFM03@FBGA80 [DX5258]
S29CD032J0JQAI00@PQFP80 [DX3020]
S29CD032J0JQAI01@PQFP80 [DX3020]
S29CD032J0JQAI02@PQFP80 [DX3020]
S29CD032J0JQAI03@PQFP80 [DX3020]
S29CD032J0JQAM00@PQFP80 [DX3020]
S29CD032J0JQAM01@PQFP80 [DX3020]
S29CD032J0JQAM02@PQFP80 [DX3020]
S29CD032J0JQAM03@PQFP80 [DX3020]
S29CD032J0JQFI00@PQFP80 [DX3020]
S29CD032J0JQFI01@PQFP80 [DX3020]
S29CD032J0JQFI02@PQFP80 [DX3020]
S29CD032J0JQFI03@PQFP80 [DX3020]
S29CD032J0JQFM00@PQFP80 [DX3020]
S29CD032J0JQFM01@PQFP80 [DX3020]
S29CD032J0JQFM02@PQFP80 [DX3020]
S29CD032J0JQFM03@PQFP80 [DX3020]
S29CD032J0MFAI00@FBGA80 [DX5258]
S29CD032J0MFAI01@FBGA80 [DX5258]
S29CD032J0MFAI02@FBGA80 [DX5258]
S29CD032J0MFAI03@FBGA80 [DX5258]
S29CD032J0MFAM00@FBGA80 [DX5258]
S29CD032J0MFAM01@FBGA80 [DX5258]
S29CD032J0MFAM02@FBGA80 [DX5258]
S29CD032J0MFAM03@FBGA80 [DX5258]
S29CD032J0MFFI00@FBGA80 [DX5258]
S29CD032J0MFFI01@FBGA80 [DX5258]
S29CD032J0MFFI02@FBGA80 [DX5258]
S29CD032J0MFFI03@FBGA80 [DX5258]
S29CD032J0MFFM00@FBGA80 [DX5258]
S29CD032J0MFFM01@FBGA80 [DX5258]
S29CD032J0MFFM02@FBGA80 [DX5258]
S29CD032J0MFFM03@FBGA80 [DX5258]
S29CD032J0MQAI00@PQFP80 [DX3020]
S29CD032J0MQAI01@PQFP80 [DX3020]
S29CD032J0MQAI02@PQFP80 [DX3020]
S29CD032J0MQAI03@PQFP80 [DX3020]
S29CD032J0MQAM00@PQFP80 [DX3020]
S29CD032J0MQAM01@PQFP80 [DX3020]
S29CD032J0MQAM02@PQFP80 [DX3020]
S29CD032J0MQAM03@PQFP80 [DX3020]
S29CD032J0MQFI00@PQFP80 [DX3020]
S29CD032J0MQFI01@PQFP80 [DX3020]
S29CD032J0MQFI02@PQFP80 [DX3020]
S29CD032J0MQFI03@PQFP80 [DX3020]
S29CD032J0MQFM00@PQFP80 [DX3020]
S29CD032J0MQFM01@PQFP80 [DX3020]
S29CD032J0MQFM02@PQFP80 [DX3020]
S29CD032J0MQFM03@PQFP80 [DX3020]
S29CD032J0PFAI00@FBGA80 [DX5258]
S29CD032J0PFAI01@FBGA80 [DX5258]
S29CD032J0PFAI02@FBGA80 [DX5258]
S29CD032J0PFAI03@FBGA80 [DX5258]
S29CD032J0PFAM00@FBGA80 [DX5258]
S29CD032J0PFAM01@FBGA80 [DX5258]
S29CD032J0PFAM02@FBGA80 [DX5258]
S29CD032J0PFAM03@FBGA80 [DX5258]
S29CD032J0PFFI00@FBGA80 [DX5258]
S29CD032J0PFFI01@FBGA80 [DX5258]
S29CD032J0PFFI02@FBGA80 [DX5258]
S29CD032J0PFFI03@FBGA80 [DX5258]
S29CD032J0PFFM00@FBGA80 [DX5258]
S29CD032J0PFFM01@FBGA80 [DX5258]
S29CD032J0PFFM02@FBGA80 [DX5258]
S29CD032J0PFFM03@FBGA80 [DX5258]
S29CD032J0PQAI00@PQFP80 [DX3020]
S29CD032J0PQAI01@PQFP80 [DX3020]
S29CD032J0PQAI02@PQFP80 [DX3020]
S29CD032J0PQAI03@PQFP80 [DX3020]
S29CD032J0PQAM00@PQFP80 [DX3020]
S29CD032J0PQAM01@PQFP80 [DX3020]
S29CD032J0PQAM02@PQFP80 [DX3020]
S29CD032J0PQAM03@PQFP80 [DX3020]
S29CD032J0PQFI00@PQFP80 [DX3020]
S29CD032J0PQFI01@PQFP80 [DX3020]

S29CD032J0PQFI02@PQFP80 [DX3020]
S29CD032J0PQFI03@PQFP80 [DX3020]
S29CD032J0PQFM00@PQFP80 [DX3020]
S29CD032J0PQFM01@PQFP80 [DX3020]
S29CD032J0PQFM02@PQFP80 [DX3020]
S29CD032J0PQFM03@PQFP80 [DX3020]
S29CD032J0RFAI00@FBGA80 [DX5258]
S29CD032J0RFAI01@FBGA80 [DX5258]
S29CD032J0RFAI02@FBGA80 [DX5258]
S29CD032J0RFAI03@FBGA80 [DX5258]
S29CD032J0RFAM00@FBGA80 [DX5258]
S29CD032J0RFAM01@FBGA80 [DX5258]
S29CD032J0RFAM02@FBGA80 [DX5258]
S29CD032J0RFAM03@FBGA80 [DX5258]
S29CD032J0RFFI00@FBGA80 [DX5258]
S29CD032J0RFFI01@FBGA80 [DX5258]
S29CD032J0RFFI02@FBGA80 [DX5258]
S29CD032J0RFFI03@FBGA80 [DX5258]
S29CD032J0RFFM00@FBGA80 [DX5258]
S29CD032J0RFFM01@FBGA80 [DX5258]
S29CD032J0RFFM02@FBGA80 [DX5258]
S29CD032J0RFFM03@FBGA80 [DX5258]
S29CD032J0RQAI00@PQFP80 [DX3020]
S29CD032J0RQAI01@PQFP80 [DX3020]
S29CD032J0RQAI02@PQFP80 [DX3020]
S29CD032J0RQAI03@PQFP80 [DX3020]
S29CD032J0RQAM00@PQFP80 [DX3020]
S29CD032J0RQAM01@PQFP80 [DX3020]
S29CD032J0RQAM02@PQFP80 [DX3020]
S29CD032J0RQAM03@PQFP80 [DX3020]
S29CD032J0RQFI00@PQFP80 [DX3020]
S29CD032J0RQFI01@PQFP80 [DX3020]
S29CD032J0RQFI02@PQFP80 [DX3020]
S29CD032J0RQFI03@PQFP80 [DX3020]
S29CD032J0RQFM00@PQFP80 [DX3020]
S29CD032J0RQFM01@PQFP80 [DX3020]
S29CD032J0RQFM02@PQFP80 [DX3020]
S29CD032J0RQFM03@PQFP80 [DX3020]
S29CD032J1JFAI00@FBGA80 [DX5258]
S29CD032J1JFAI01@FBGA80 [DX5258]
S29CD032J1JFAI02@FBGA80 [DX5258]
S29CD032J1JFAI03@FBGA80 [DX5258]
S29CD032J1JFAM00@FBGA80 [DX5258]
S29CD032J1JFAM01@FBGA80 [DX5258]
S29CD032J1JFAM02@FBGA80 [DX5258]
S29CD032J1JFAM03@FBGA80 [DX5258]
S29CD032J1JFFI00@FBGA80 [DX5258]
S29CD032J1JFFI01@FBGA80 [DX5258]
S29CD032J1JFFI02@FBGA80 [DX5258]
S29CD032J1JFFI03@FBGA80 [DX5258]
S29CD032J1JFFM00@FBGA80 [DX5258]
S29CD032J1JFFM01@FBGA80 [DX5258]
S29CD032J1JFFM02@FBGA80 [DX5258]
S29CD032J1JFFM03@FBGA80 [DX5258]
S29CD032J1JQAI00@PQFP80 [DX3020]
S29CD032J1JQAI01@PQFP80 [DX3020]
S29CD032J1JQAI02@PQFP80 [DX3020]
S29CD032J1JQAI03@PQFP80 [DX3020]
S29CD032J1JQAM00@PQFP80 [DX3020]
S29CD032J1JQAM01@PQFP80 [DX3020]
S29CD032J1JQAM02@PQFP80 [DX3020]
S29CD032J1JQAM03@PQFP80 [DX3020]
S29CD032J1JQFI00@PQFP80 [DX3020]
S29CD032J1JQFI01@PQFP80 [DX3020]
S29CD032J1JQFI02@PQFP80 [DX3020]
S29CD032J1JQFI03@PQFP80 [DX3020]
S29CD032J1JQFM00@PQFP80 [DX3020]
S29CD032J1JQFM01@PQFP80 [DX3020]
S29CD032J1JQFM02@PQFP80 [DX3020]
S29CD032J1JQFM03@PQFP80 [DX3020]
S29CL016J1MFAI02@FBGA80 [DX5258]
S29CL016J1MFAI03@FBGA80 [DX5258]
S29CL016J1MFAI12@FBGA80 [DX5258]
S29CL016J1MFAI13@FBGA80 [DX5258]
S29CL016J1MFAM02@FBGA80 [DX5258]
S29CL016J1MFAM03@FBGA80 [DX5258]
S29CL016J1MFAM12@FBGA80 [DX5258]
S29CL016J1MFAM13@FBGA80 [DX5258]
S29CL016J1MFFI02@FBGA80 [DX5258]
S29CL016J1MFFI03@FBGA80 [DX5258]
S29CL016J1MFFI12@FBGA80 [DX5258]
S29CL016J1MFFI13@FBGA80 [DX5258]
S29CL016J1MFFM02@FBGA80 [DX5258]
S29CL016J1MFFM03@FBGA80 [DX5258]
S29CL016J1MFFM12@FBGA80 [DX5258]
S29CL016J1MFFM13@FBGA80 [DX5258]
S29CL016J1MQAI02@PQFP80 [DX3020]
S29CL016J1MQAI03@PQFP80 [DX3020]
S29CL016J1MQAI12@PQFP80 [DX3020]
S29CL016J1MQAI13@PQFP80 [DX3020]
S29CL016J1MQAM02@PQFP80 [DX3020]
S29CL016J1MQAM03@PQFP80 [DX3020]
S29CL016J1MQAM12@PQFP80 [DX3020]
S29CL016J1MQAM13@PQFP80 [DX3020]
S29CL016J1MQFI02@PQFP80 [DX3020]
S29CL016J1MQFI03@PQFP80 [DX3020]

S29CL016J1MQFI12@PQFP80 [DX3020]
S29CL016J1MQFI13@PQFP80 [DX3020]
S29CL016J1MQFM02@PQFP80 [DX3020]
S29CL016J1MQFM03@PQFP80 [DX3020]
S29CL016J1MQFM12@PQFP80 [DX3020]
S29CL016J1MQFM13@PQFP80 [DX3020]
S29CL032J0JFAI00@FBGA80 [DX5258]
S29CL032J0JFAI01@FBGA80 [DX5258]
S29CL032J0JFAI02@FBGA80 [DX5258]
S29CL032J0JFAI03@FBGA80 [DX5258]
S29CL032J0JFAM00@FBGA80 [DX5258]
S29CL032J0JFAM01@FBGA80 [DX5258]
S29CL032J0JFAM02@FBGA80 [DX5258]
S29CL032J0JFAM03@FBGA80 [DX5258]
S29CL032J0JFFI00@FBGA80 [DX5258]
S29CL032J0JFFI01@FBGA80 [DX5258]
S29CL032J0JFFI02@FBGA80 [DX5258]
S29CL032J0JFFI03@FBGA80 [DX5258]
S29CL032J0JFFM00@FBGA80 [DX5258]
S29CL032J0JFFM01@FBGA80 [DX5258]
S29CL032J0JFFM02@FBGA80 [DX5258]
S29CL032J0JFFM03@FBGA80 [DX5258]
S29CL032J0JQAI00@PQFP80 [DX3020]
S29CL032J0JQAI01@PQFP80 [DX3020]
S29CL032J0JQAI02@PQFP80 [DX3020]
S29CL032J0JQAI03@PQFP80 [DX3020]
S29CL032J0JQAM00@PQFP80 [DX3020]
S29CL032J0JQAM01@PQFP80 [DX3020]
S29CL032J0JQAM02@PQFP80 [DX3020]
S29CL032J0JQAM03@PQFP80 [DX3020]
S29CL032J0JQFI00@PQFP80 [DX3020]
S29CL032J0JQFI01@PQFP80 [DX3020]
S29CL032J0JQFI02@PQFP80 [DX3020]
S29CL032J0JQFI03@PQFP80 [DX3020]
S29CL032J0JQFM00@PQFP80 [DX3020]
S29CL032J0JQFM01@PQFP80 [DX3020]
S29CL032J0JQFM02@PQFP80 [DX3020]
S29CL032J0JQFM03@PQFP80 [DX3020]
S29CL032J0MFAI00@FBGA80 [DX5258]
S29CL032J0MFAI01@FBGA80 [DX5258]
S29CL032J0MFAI02@FBGA80 [DX5258]
S29CL032J0MFAI03@FBGA80 [DX5258]
S29CL032J0MFAM00@FBGA80 [DX5258]
S29CL032J0MFAM01@FBGA80 [DX5258]
S29CL032J0MFAM02@FBGA80 [DX5258]
S29CL032J0MFAM03@FBGA80 [DX5258]
S29CL032J0MFFI00@FBGA80 [DX5258]
S29CL032J0MFFI01@FBGA80 [DX5258]
S29CL032J0MFFI02@FBGA80 [DX5258]
S29CL032J0MFFI03@FBGA80 [DX5258]
S29CL032J0MFFM00@FBGA80 [DX5258]
S29CL032J0MFFM01@FBGA80 [DX5258]
S29CL032J0MFFM02@FBGA80 [DX5258]
S29CL032J0MFFM03@FBGA80 [DX5258]
S29CL032J0MQAI00@PQFP80 [DX3020]
S29CL032J0MQAI01@PQFP80 [DX3020]
S29CL032J0MQAI02@PQFP80 [DX3020]
S29CL032J0MQAI03@PQFP80 [DX3020]
S29CL032J0MQAM00@PQFP80 [DX3020]
S29CL032J0MQAM01@PQFP80 [DX3020]
S29CL032J0MQAM02@PQFP80 [DX3020]
S29CL032J0MQAM03@PQFP80 [DX3020]
S29CL032J0MQFI00@PQFP80 [DX3020]
S29CL032J0MQFI01@PQFP80 [DX3020]
S29CL032J0MQFI02@PQFP80 [DX3020]
S29CL032J0MQFI03@PQFP80 [DX3020]
S29CL032J0MQFM00@PQFP80 [DX3020]
S29CL032J0MQFM01@PQFP80 [DX3020]
S29CL032J0MQFM02@PQFP80 [DX3020]
S29CL032J0MQFM03@PQFP80 [DX3020]
S29CL032J0PFAI00@FBGA80 [DX5258]
S29CL032J0PFAI01@FBGA80 [DX5258]
S29CL032J0PFAI02@FBGA80 [DX5258]
S29CL032J0PFAI03@FBGA80 [DX5258]
S29CL032J0PFAM00@FBGA80 [DX5258]
S29CL032J0PFAM01@FBGA80 [DX5258]
S29CL032J0PFAM02@FBGA80 [DX5258]
S29CL032J0PFAM03@FBGA80 [DX5258]
S29CL032J0PFFI00@FBGA80 [DX5258]
S29CL032J0PFFI01@FBGA80 [DX5258]
S29CL032J0PFFI02@FBGA80 [DX5258]
S29CL032J0PFFI03@FBGA80 [DX5258]
S29CL032J0PFFM00@FBGA80 [DX5258]
S29CL032J0PFFM01@FBGA80 [DX5258]
S29CL032J0PFFM02@FBGA80 [DX5258]
S29CL032J0PFFM03@FBGA80 [DX5258]
S29CL032J0PQAI00@PQFP80 [DX3020]
S29CL032J0PQAI01@PQFP80 [DX3020]
S29CL032J0PQAI02@PQFP80 [DX3020]
S29CL032J0PQAI03@PQFP80 [DX3020]
S29CL032J0PQAM00@PQFP80 [DX3020]
S29CL032J0PQAM01@PQFP80 [DX3020]
S29CL032J0PQAM02@PQFP80 [DX3020]
S29CL032J0PQAM03@PQFP80 [DX3020]
S29CL032J0PQFI00@PQFP80 [DX3020]
S29CL032J0PQFI01@PQFP80 [DX3020]

S29CL032J0PQFI02@PQFP80 [DX3020]
S29CL032J0PQFI03@PQFP80 [DX3020]
S29CL032J0PQFM00@PQFP80 [DX3020]
S29CL032J0PQFM01@PQFP80 [DX3020]
S29CL032J0PQFM02@PQFP80 [DX3020]
S29CL032J0PQFM03@PQFP80 [DX3020]
S29CL032J0RFAI00@FBGA80 [DX5258]
S29CL032J0RFAI01@FBGA80 [DX5258]
S29CL032J0RFAI02@FBGA80 [DX5258]
S29CL032J0RFAI03@FBGA80 [DX5258]
S29CL032J0RFAM00@FBGA80 [DX5258]
S29CL032J0RFAM01@FBGA80 [DX5258]
S29CL032J0RFAM02@FBGA80 [DX5258]
S29CL032J0RFAM03@FBGA80 [DX5258]
S29CL032J0RFFI00@FBGA80 [DX5258]
S29CL032J0RFFI01@FBGA80 [DX5258]
S29CL032J0RFFI02@FBGA80 [DX5258]
S29CL032J0RFFI03@FBGA80 [DX5258]
S29CL032J0RFFM00@FBGA80 [DX5258]
S29CL032J0RFFM01@FBGA80 [DX5258]
S29CL032J0RFFM02@FBGA80 [DX5258]
S29CL032J0RFFM03@FBGA80 [DX5258]
S29CL032J0RQAI00@PQFP80 [DX3020]
S29CL032J0RQAI01@PQFP80 [DX3020]
S29CL032J0RQAI02@PQFP80 [DX3020]
S29CL032J0RQAI03@PQFP80 [DX3020]
S29CL032J0RQAM00@PQFP80 [DX3020]
S29CL032J0RQAM01@PQFP80 [DX3020]
S29CL032J0RQAM02@PQFP80 [DX3020]
S29CL032J0RQAM03@PQFP80 [DX3020]
S29CL032J0RQFI00@PQFP80 [DX3020]
S29CL032J0RQFI01@PQFP80 [DX3020]
S29CL032J0RQFI02@PQFP80 [DX3020]
S29CL032J0RQFI03@PQFP80 [DX3020]
S29CL032J0RQFM00@PQFP80 [DX3020]
S29CL032J0RQFM01@PQFP80 [DX3020]
S29CL032J0RQFM02@PQFP80 [DX3020]
S29CL032J0RQFM03@PQFP80 [DX3020]
S29CL032J1JFAI00@FBGA80 [DX5258]
S29CL032J1JFAI01@FBGA80 [DX5258]
S29CL032J1JFAI02@FBGA80 [DX5258]
S29CL032J1JFAI03@FBGA80 [DX5258]
S29CL032J1JFAM00@FBGA80 [DX5258]
S29CL032J1JFAM01@FBGA80 [DX5258]
S29CL032J1JFAM02@FBGA80 [DX5258]
S29CL032J1JFAM03@FBGA80 [DX5258]
S29CL032J1JFFI00@FBGA80 [DX5258]
S29CL032J1JFFI01@FBGA80 [DX5258]
S29CL032J1JFFI02@FBGA80 [DX5258]
S29CL032J1JFFI03@FBGA80 [DX5258]
S29CL032J1JFFM00@FBGA80 [DX5258]
S29CL032J1JFFM01@FBGA80 [DX5258]
S29CL032J1JFFM02@FBGA80 [DX5258]
S29CL032J1JFFM03@FBGA80 [DX5258]
S29CL032J1JQAI00@PQFP80 [DX3020]
S29CL032J1JQAI01@PQFP80 [DX3020]
S29CL032J1JQAI02@PQFP80 [DX3020]
S29CL032J1JQAI03@PQFP80 [DX3020]
S29CL032J1JQAM00@PQFP80 [DX3020]
S29CL032J1JQAM01@PQFP80 [DX3020]
S29CL032J1JQAM02@PQFP80 [DX3020]
S29CL032J1JQAM03@PQFP80 [DX3020]
S29CL032J1JQFI00@PQFP80 [DX3020]
S29CL032J1JQFI01@PQFP80 [DX3020]
S29CL032J1JQFI02@PQFP80 [DX3020]
S29CL032J1JQFI03@PQFP80 [DX3020]
S29CL032J1JQFM00@PQFP80 [DX3020]
S29CL032J1JQFM01@PQFP80 [DX3020]
S29CL032J1JQFM02@PQFP80 [DX3020]
S29CL032J1JQFM03@PQFP80 [DX3020]
S29GL016A10BAI01@FBGA48 [DX5043]
S29GL016A10BAI02@FBGA48 [DX5043]
S29GL016A10BAI03@FBGA48 [DX5043]
S29GL016A10BAI04@FBGA48 [DX5043]
S29GL016A10BAIR1@FBGA48 [DX5043]
S29GL016A10BAIR2@FBGA48 [DX5043]
S29GL016A10BAIR3@FBGA48 [DX5043]
S29GL016A10BAIR4@FBGA48 [DX5043]
S29GL016A10BAIW1@FBGA56 [DX5045]
S29GL016A10BAIW2@FBGA56 [DX5045]
S29GL016A10BFI01@FBGA48 [DX5043]
S29GL016A10BFI02@FBGA48 [DX5043]
S29GL016A10BFI03@FBGA48 [DX5043]
S29GL016A10BFI04@FBGA48 [DX5043]
S29GL016A10BFIR1@FBGA48 [DX5043]
S29GL016A10BFIR2@FBGA48 [DX5043]
S29GL016A10BFIR3@FBGA48 [DX5043]
S29GL016A10BFIR4@FBGA48 [DX5043]
S29GL016A10BFIW1@FBGA56 [DX5045]
S29GL016A10BFIW2@FBGA56 [DX5045]
S29GL016A10FAI01@FBGA64 [DX5074]
S29GL016A10FAI02@FBGA64 [DX5074]
S29GL016A10FAI03@FBGA64 [DX5074]
S29GL016A10FAI04@FBGA64 [DX5074]
S29GL016A10FAIR1@FBGA64 [DX5074]
S29GL016A10FAIR2@FBGA64 [DX5074]

S29GL016A10FAIR3@FBGA64 [DX5074]
S29GL016A10FAIR4@FBGA64 [DX5074]
S29GL016A10FFI01@FBGA64 [DX5074]
S29GL016A10FFI02@FBGA64 [DX5074]
S29GL016A10FFI03@FBGA64 [DX5074]
S29GL016A10FFI04@FBGA64 [DX5074]
S29GL016A10FFIR1@FBGA64 [DX5074]
S29GL016A10FFIR2@FBGA64 [DX5074]
S29GL016A10FFIR3@FBGA64 [DX5074]
S29GL016A10FFIR4@FBGA64 [DX5074]
S29GL016A10TAI01@TSOP48 [DX1004]
S29GL016A10TAI02@TSOP48 [DX1004]
S29GL016A10TAI03@TSOP48 [DX1004]
S29GL016A10TAI04@TSOP48 [DX1004]
S29GL016A10TAIR1@TSOP48 [DX1004]
S29GL016A10TAIR2@TSOP48 [DX1004]
S29GL016A10TAIR3@TSOP48 [DX1004]
S29GL016A10TAIR4@TSOP48 [DX1004]
S29GL016A10TFI01@TSOP48 [DX1004]
S29GL016A10TFI02@TSOP48 [DX1004]
S29GL016A10TFI03@TSOP48 [DX1004]
S29GL016A10TFI04@TSOP48 [DX1004]
S29GL016A10TFIR1@TSOP48 [DX1004]
S29GL016A10TFIR2@TSOP48 [DX1004]
S29GL016A10TFIR3@TSOP48 [DX1004]
S29GL016A10TFIR4@TSOP48 [DX1004]
S29GL016A90BAIR1@FBGA48 [DX5043]
S29GL016A90BAIR2@FBGA48 [DX5043]
S29GL016A90BAIR3@FBGA48 [DX5043]
S29GL016A90BAIR4@FBGA48 [DX5043]
S29GL016A90BFIR1@FBGA48 [DX5043]
S29GL016A90BFIR2@FBGA48 [DX5043]
S29GL016A90BFIR3@FBGA48 [DX5043]
S29GL016A90BFIR4@FBGA48 [DX5043]
S29GL016A90FAIR1@FBGA64 [DX5074]
S29GL016A90FAIR2@FBGA64 [DX5074]
S29GL016A90FAIR3@FBGA64 [DX5074]
S29GL016A90FAIR4@FBGA64 [DX5074]
S29GL016A90FFIR1@FBGA64 [DX5074]
S29GL016A90FFIR2@FBGA64 [DX5074]
S29GL016A90FFIR3@FBGA64 [DX5074]
S29GL016A90FFIR4@FBGA64 [DX5074]
S29GL016A90TAIR1@TSOP48 [DX1004]
S29GL016A90TAIR2@TSOP48 [DX1004]
S29GL016A90TAIR3@TSOP48 [DX1004]
S29GL016A90TAIR4@TSOP48 [DX1004]
S29GL016A90TFIR1@TSOP48 [DX1004]
S29GL016A90TFIR2@TSOP48 [DX1004]
S29GL016A90TFIR3@TSOP48 [DX1004]
S29GL016A90TFIR4@TSOP48 [DX1004]
S29GL01GP10FAI01@FBGA64 [DX5074]
S29GL01GP10FAI02@FBGA64 [DX5074]
S29GL01GP10FFI01@FBGA64 [DX5074]
S29GL01GP10FFI02@FBGA64 [DX5074]
S29GL01GP10TAI01@TSOP56 [DX1011]
S29GL01GP10TAI02@TSOP56 [DX1011]
S29GL01GP10TFI01@TSOP56 [DX1011]
S29GL01GP10TFI02@TSOP56 [DX1011]
S29GL01GP11FACR1@FBGA64 [DX5074]
S29GL01GP11FACR2@FBGA64 [DX5074]
S29GL01GP11FAI01@FBGA64 [DX5074]
S29GL01GP11FAI02@FBGA64 [DX5074]
S29GL01GP11FAIR1@FBGA64 [DX5074]
S29GL01GP11FAIR2@FBGA64 [DX5074]
S29GL01GP11FAIS7@FBGA64 [DX5074]
S29GL01GP11FAIS8@FBGA64 [DX5074]
S29GL01GP11FAIV1@FBGA64 [DX5074]
S29GL01GP11FAIV2@FBGA64 [DX5074]
S29GL01GP11FASS7@FBGA64 [DX5074]
S29GL01GP11FASS8@FBGA64 [DX5074]
S29GL01GP11FFCR1@FBGA64 [DX5074]
S29GL01GP11FFCR2@FBGA64 [DX5074]
S29GL01GP11FFI01@FBGA64 [DX5074]
S29GL01GP11FFI02@FBGA64 [DX5074]
S29GL01GP11FFIR1@FBGA64 [DX5074]
S29GL01GP11FFIR2@FBGA64 [DX5074]
S29GL01GP11FFIS7@FBGA64 [DX5074]
S29GL01GP11FFIS8@FBGA64 [DX5074]
S29GL01GP11FFIV1@FBGA64 [DX5074]
S29GL01GP11FFIV2@FBGA64 [DX5074]
S29GL01GP11FFSS7@FBGA64 [DX5074]
S29GL01GP11FFSS8@FBGA64 [DX5074]
S29GL01GP11TACR1@TSOP56 [DX1011]
S29GL01GP11TACR2@TSOP56 [DX1011]
S29GL01GP11TAI01@TSOP56 [DX1011]
S29GL01GP11TAI02@TSOP56 [DX1011]
S29GL01GP11TAIR1@TSOP56 [DX1011]
S29GL01GP11TAIR2@TSOP56 [DX1011]
S29GL01GP11TAIV1@TSOP56 [DX1011]
S29GL01GP11TAIV2@TSOP56 [DX1011]
S29GL01GP11TFCR1@TSOP56 [DX1011]
S29GL01GP11TFCR2@TSOP56 [DX1011]
S29GL01GP11TFI01@TSOP56 [DX1011]
S29GL01GP11TFI02@TSOP56 [DX1011]
S29GL01GP11TFIR1@TSOP56 [DX1011]
S29GL01GP11TFIR2@TSOP56 [DX1011]

S29GL01GP11TFIV1@TSOP56 [DX1011]
S29GL01GP11TFIV2@TSOP56 [DX1011]
S29GL01GP12FAI01@FBGA64 [DX5074]
S29GL01GP12FAI02@FBGA64 [DX5074]
S29GL01GP12FAIS1@FBGA64 [DX5074]
S29GL01GP12FAIS2@FBGA64 [DX5074]
S29GL01GP12FAIV1@FBGA64 [DX5074]
S29GL01GP12FAIV2@FBGA64 [DX5074]
S29GL01GP12FFI01@FBGA64 [DX5074]
S29GL01GP12FFI02@FBGA64 [DX5074]
S29GL01GP12FFIS1@FBGA64 [DX5074]
S29GL01GP12FFIS2@FBGA64 [DX5074]
S29GL01GP12FFIV1@FBGA64 [DX5074]
S29GL01GP12FFIV2@FBGA64 [DX5074]
S29GL01GP12TAI01@TSOP56 [DX1011]
S29GL01GP12TAI02@TSOP56 [DX1011]
S29GL01GP12TAIV1@TSOP56 [DX1011]
S29GL01GP12TAIV2@TSOP56 [DX1011]
S29GL01GP12TFI01@TSOP56 [DX1011]
S29GL01GP12TFI02@TSOP56 [DX1011]
S29GL01GP12TFIV1@TSOP56 [DX1011]
S29GL01GP12TFIV2@TSOP56 [DX1011]
S29GL01GP13FAI01@FBGA64 [DX5074]
S29GL01GP13FAI02@FBGA64 [DX5074]
S29GL01GP13FAIS5@FBGA64 [DX5074]
S29GL01GP13FAIS6@FBGA64 [DX5074]
S29GL01GP13FAIV1@FBGA64 [DX5074]
S29GL01GP13FAIV2@FBGA64 [DX5074]
S29GL01GP13FFI01@FBGA64 [DX5074]
S29GL01GP13FFI02@FBGA64 [DX5074]
S29GL01GP13FFIS5@FBGA64 [DX5074]
S29GL01GP13FFIS6@FBGA64 [DX5074]
S29GL01GP13FFIV1@FBGA64 [DX5074]
S29GL01GP13FFIV2@FBGA64 [DX5074]
S29GL01GP13TAI01@TSOP56 [DX1011]
S29GL01GP13TAI02@TSOP56 [DX1011]
S29GL01GP13TAIV1@TSOP56 [DX1011]
S29GL01GP13TAIV2@TSOP56 [DX1011]
S29GL01GP13TFI01@TSOP56 [DX1011]
S29GL01GP13TFI02@TSOP56 [DX1011]
S29GL01GP13TFIV1@TSOP56 [DX1011]
S29GL01GP13TFIV2@TSOP56 [DX1011]
S29GL01GP90FAI01@FBGA64 [DX5074]
S29GL01GP90FAI02@FBGA64 [DX5074]
S29GL01GP90FFI01@FBGA64 [DX5074]
S29GL01GP90FFI02@FBGA64 [DX5074]
S29GL01GP90TAI01@TSOP56 [DX1011]
S29GL01GP90TAI02@TSOP56 [DX1011]
S29GL01GP90TFI01@TSOP56 [DX1011]
S29GL01GP90TFI02@TSOP56 [DX1011]
S29GL01GR11FFCR1@FBGA64 [DX5103]
S29GL01GR11FFCR2@FBGA64 [DX5103]
S29GL01GR11FFCS7@FBGA64 [DX5103]
S29GL01GR11FFCS8@FBGA64 [DX5103]
S29GL01GR11FFIR1@FBGA64 [DX5103]
S29GL01GR11FFIR2@FBGA64 [DX5103]
S29GL01GR11TFCR1@TSOP56 [DX1011]
S29GL01GR11TFCR2@TSOP56 [DX1011]
S29GL01GR11TFIR1@TSOP56 [DX1011]
S29GL01GR11TFIR2@TSOP56 [DX1011]
S29GL01GR12DFI01@FBGA64 [DX5074]
S29GL01GR12DFI02@FBGA64 [DX5074]
S29GL01GR12TFI01@TSOP56 [DX1011]
S29GL01GR12TFI02@TSOP56 [DX1011]
S29GL01GR13DFIV1@FBGA64 [DX5074]
S29GL01GR13DFIV2@FBGA64 [DX5074]
S29GL01GR13TFIV1@TSOP56 [DX1011]
S29GL01GR13TFIV2@TSOP56 [DX1011]
S29GL01GS10DHI01@FBGA64 [DX5103]
S29GL01GS10DHI02@FBGA64 [DX5103]
S29GL01GS10DHSS1@FBGA64 [DX5103]
S29GL01GS10DHSS2@FBGA64 [DX5103]
S29GL01GS10DHSS3 [DX5103]
S29GL01GS10DHSS4 [DX5103]
S29GL01GS10DHSS5@FBGA64 [DX5103]
S29GL01GS10DHSS6@FBGA64 [DX5103]
S29GL01GS10DHSS7 [DX5103]
S29GL01GS10DHSS8 [DX5103]
S29GL01GS10FHI01@FBGA64 [DX5074]
S29GL01GS10FHI02@FBGA64 [DX5074]
S29GL01GS10FHSS1@FBGA64 [DX5074]
S29GL01GS10FHSS2@FBGA64 [DX5074]
S29GL01GS10FHSS3 [DX5074]
S29GL01GS10FHSS4 [DX5074]
S29GL01GS10FHSS5@FBGA64 [DX5074]
S29GL01GS10FHSS6@FBGA64 [DX5074]
S29GL01GS10FHSS7 [DX5074]
S29GL01GS10FHSS8 [DX5074]
S29GL01GS10TFI01@TSOP56 [DX1011]
S29GL01GS10TFI02@TSOP56 [DX1011]
S29GL01GS11DHI01@FBGA64 [DX5103]
S29GL01GS11DHI02@FBGA64 [DX5103]
S29GL01GS11DHIV1@FBGA64 [DX5103]
S29GL01GS11DHIV2@FBGA64 [DX5103]
S29GL01GS11DHSS1@FBGA64 [DX5103]
S29GL01GS11DHSS2@FBGA64 [DX5103]

S29GL01GS11DHSS3 [DX5103]
S29GL01GS11DHSS4 [DX5103]
S29GL01GS11DHSS5@FBGA64 [DX5103]
S29GL01GS11DHSS6@FBGA64 [DX5103]
S29GL01GS11DHSS7 [DX5103]
S29GL01GS11DHSS8 [DX5103]
S29GL01GS11FHI01@FBGA64 [DX5074]
S29GL01GS11FHI02@FBGA64 [DX5074]
S29GL01GS11FHIV1@FBGA64 [DX5074]
S29GL01GS11FHIV2@FBGA64 [DX5074]
S29GL01GS11FHSS1@FBGA64 [DX5074]
S29GL01GS11FHSS2@FBGA64 [DX5074]
S29GL01GS11FHSS3 [DX5074]
S29GL01GS11FHSS4 [DX5074]
S29GL01GS11FHSS5@FBGA64 [DX5074]
S29GL01GS11FHSS6@FBGA64 [DX5074]
S29GL01GS11FHSS7 [DX5074]
S29GL01GS11FHSS8 [DX5074]
S29GL01GS11TFI01@TSOP56 [DX1011]
S29GL01GS11TFI02@TSOP56 [DX1011]
S29GL01GS11TFIV1@TSOP56 [DX1011]
S29GL01GS11TFIV2@TSOP56 [DX1011]
S29GL01GS12DHIV1@FBGA64 [DX5103]
S29GL01GS12DHIV2@FBGA64 [DX5103]
S29GL01GS12FHIV1@FBGA64 [DX5074]
S29GL01GS12FHIV2@FBGA64 [DX5074]
S29GL01GS12TFIV1@TSOP56 [DX1011]
S29GL01GS12TFIV2@TSOP56 [DX1011]
S29GL032A10BAIR3@FBGA48 [DX5043]
S29GL032A10BAIR4@FBGA48 [DX5043]
S29GL032A10BAIW3@FBGA56 [DX5045]
S29GL032A10BAIW4@FBGA56 [DX5045]
S29GL032A10BFIR3@FBGA48 [DX5043]
S29GL032A10BFIR4@FBGA48 [DX5043]
S29GL032A10BFIW3@FBGA56 [DX5045]
S29GL032A10BFIW4@FBGA56 [DX5045]
S29GL032A10FAIR1@FBGA64 [DX5074]
S29GL032A10FAIR2@FBGA64 [DX5074]
S29GL032A10FAIR3@FBGA64 [DX5074]
S29GL032A10FAIR4@FBGA64 [DX5074]
S29GL032A10FFIR1@FBGA64 [DX5074]
S29GL032A10FFIR2@FBGA64 [DX5074]
S29GL032A10FFIR3@FBGA64 [DX5074]
S29GL032A10FFIR4@FBGA64 [DX5074]
S29GL032A10TAIR1@TSOP56 [DX1011]
S29GL032A10TAIR2@TSOP56 [DX1011]
S29GL032A10TAIR3@TSOP48 [DX1004]
S29GL032A10TAIR4@TSOP48 [DX1004]
S29GL032A10TFIR1@TSOP56 [DX1011]
S29GL032A10TFIR2@TSOP56 [DX1011]
S29GL032A10TFIR3@TSOP48 [DX1004]
S29GL032A10TFIR4@TSOP48 [DX1004]
S29GL032A11BAIR3@FBGA48 [DX5043]
S29GL032A11BAIR4@FBGA48 [DX5043]
S29GL032A11BAIW3@FBGA56 [DX5045]
S29GL032A11BAIW4@FBGA56 [DX5045]
S29GL032A11BFIR3@FBGA48 [DX5043]
S29GL032A11BFIR4@FBGA48 [DX5043]
S29GL032A11BFIW3@FBGA56 [DX5045]
S29GL032A11BFIW4@FBGA56 [DX5045]
S29GL032A11FAIR1@FBGA64 [DX5074]
S29GL032A11FAIR2@FBGA64 [DX5074]
S29GL032A11FAIR3@FBGA64 [DX5074]
S29GL032A11FAIR4@FBGA64 [DX5074]
S29GL032A11FAIS1@FBGA64 [DX5074]
S29GL032A11FAIS2@FBGA64 [DX5074]
S29GL032A11FAIS3@FBGA64 [DX5004]
S29GL032A11FAIS4@FBGA64 [DX5004]
S29GL032A11FFIR1@FBGA64 [DX5074]
S29GL032A11FFIR2@FBGA64 [DX5074]
S29GL032A11FFIR3@FBGA64 [DX5074]
S29GL032A11FFIR4@FBGA64 [DX5074]
S29GL032A11FFIS1@FBGA64 [DX5074]
S29GL032A11FFIS2@FBGA64 [DX5074]
S29GL032A11FFIS3@FBGA64 [DX5004]
S29GL032A11FFIS4@FBGA64 [DX5004]
S29GL032A11TAIR1@TSOP56 [DX1011]
S29GL032A11TAIR2@TSOP56 [DX1011]
S29GL032A11TAIR3@TSOP48 [DX1004]
S29GL032A11TAIR4@TSOP48 [DX1004]
S29GL032A11TFIR1@TSOP56 [DX1011]
S29GL032A11TFIR2@TSOP56 [DX1011]
S29GL032A11TFIR3@TSOP48 [DX1004]
S29GL032A11TFIR4@TSOP48 [DX1004]
S29GL032A90BAIR3@FBGA48 [DX5043]
S29GL032A90BAIR4@FBGA48 [DX5043]
S29GL032A90BFIR3@FBGA48 [DX5043]
S29GL032A90BFIR4@FBGA48 [DX5043]
S29GL032A90FAIR1@FBGA64 [DX5074]
S29GL032A90FAIR2@FBGA64 [DX5074]
S29GL032A90FAIR3@FBGA64 [DX5074]
S29GL032A90FAIR4@FBGA64 [DX5074]
S29GL032A90FAIS1@FBGA64 [DX5074]
S29GL032A90FAIS2@FBGA64 [DX5074]
S29GL032A90FAIS3@FBGA64 [DX5004]
S29GL032A90FAIS4@FBGA64 [DX5004]

S29GL032A90FFIR1@FBGA64 [DX5074]
S29GL032A90FFIR2@FBGA64 [DX5074]
S29GL032A90FFIR3@FBGA64 [DX5074]
S29GL032A90FFIR4@FBGA64 [DX5074]
S29GL032A90FFIS1@FBGA64 [DX5074]
S29GL032A90FFIS2@FBGA64 [DX5074]
S29GL032A90FFIS3@FBGA64 [DX5004]
S29GL032A90FFIS4@FBGA64 [DX5004]
S29GL032A90TAIR1@TSOP56 [DX1011]
S29GL032A90TAIR2@TSOP56 [DX1011]
S29GL032A90TAIR3@TSOP48 [DX1004]
S29GL032A90TAIR4@TSOP48 [DX1004]
S29GL032A90TFIR1@TSOP56 [DX1011]
S29GL032A90TFIR2@TSOP56 [DX1011]
S29GL032A90TFIR3@TSOP48 [DX1004]
S29GL032A90TFIR4@TSOP48 [DX1004]
S29GL032M10BAIR0@FBGA48 [DX5022]
S29GL032M10BAIR3@FBGA48 [DX5022]
S29GL032M10BAIR4@FBGA48 [DX5022]
S29GL032M10BAIR5@FBGA48 [DX5002]
S29GL032M10BAIR6@FBGA48 [DX5002]
S29GL032M10BFIR0@FBGA48 [DX5022]
S29GL032M10BFIR3@FBGA48 [DX5022]
S29GL032M10BFIR4@FBGA48 [DX5022]
S29GL032M10BFIR5@FBGA48 [DX5002]
S29GL032M10BFIR6@FBGA48 [DX5002]
S29GL032M10FAIR1@FBGA64 [DX5074]
S29GL032M10FAIR2@FBGA64 [DX5074]
S29GL032M10FAIR3@FBGA64 [DX5074]
S29GL032M10FAIR4@FBGA64 [DX5074]
S29GL032M10FFIR1@FBGA64 [DX5074]
S29GL032M10FFIR2@FBGA64 [DX5074]
S29GL032M10FFIR3@FBGA64 [DX5074]
S29GL032M10FFIR4@FBGA64 [DX5074]
S29GL032M10TAIR0@FBGA48 [DX1006]
S29GL032M10TAIR1@TSOP56 [DX1011]
S29GL032M10TAIR2@TSOP56 [DX1011]
S29GL032M10TAIR3@TSOP48 [DX1004]
S29GL032M10TAIR4@TSOP48 [DX1004]
S29GL032M10TBIR3@TSOP48 [DX1004]
S29GL032M10TBIR4@TSOP48 [DX1004]
S29GL032M10TCIR3@TSOP48 [DX1004]
S29GL032M10TCIR4@TSOP48 [DX1004]
S29GL032M10TFIR0@FBGA48 [DX1006]
S29GL032M10TFIR1@TSOP56 [DX1011]
S29GL032M10TFIR2@TSOP56 [DX1011]
S29GL032M10TFIR3@TSOP48 [DX1004]
S29GL032M10TFIR4@TSOP48 [DX1004]
S29GL032M11BAIR0@FBGA48 [DX5022]
S29GL032M11BAIR3@FBGA48 [DX5022]
S29GL032M11BAIR4@FBGA48 [DX5022]
S29GL032M11BAIR5@FBGA48 [DX5002]
S29GL032M11BAIR6@FBGA48 [DX5002]
S29GL032M11BFIR0@FBGA48 [DX5022]
S29GL032M11BFIR3@FBGA48 [DX5022]
S29GL032M11BFIR4@FBGA48 [DX5022]
S29GL032M11BFIR5@FBGA48 [DX5002]
S29GL032M11BFIR6@FBGA48 [DX5002]
S29GL032M11FACS1@FBGA64 [DX5074]
S29GL032M11FACS2@FBGA64 [DX5074]
S29GL032M11FACS3@FBGA64 [DX5004]
S29GL032M11FACS4@FBGA64 [DX5004]
S29GL032M11FAIR1@FBGA64 [DX5074]
S29GL032M11FAIR2@FBGA64 [DX5074]
S29GL032M11FAIR3@FBGA64 [DX5074]
S29GL032M11FAIR4@FBGA64 [DX5074]
S29GL032M11FAIS1@FBGA64 [DX5074]
S29GL032M11FAIS2@FBGA64 [DX5074]
S29GL032M11FAIS3@FBGA64 [DX5004]
S29GL032M11FAIS4@FBGA64 [DX5004]
S29GL032M11FFCS1@FBGA64 [DX5074]
S29GL032M11FFCS2@FBGA64 [DX5074]
S29GL032M11FFCS3@FBGA64 [DX5004]
S29GL032M11FFCS4@FBGA64 [DX5004]
S29GL032M11FFIR1@FBGA64 [DX5074]
S29GL032M11FFIR2@FBGA64 [DX5074]
S29GL032M11FFIR3@FBGA64 [DX5074]
S29GL032M11FFIR4@FBGA64 [DX5074]
S29GL032M11FFIS1@FBGA64 [DX5074]
S29GL032M11FFIS2@FBGA64 [DX5074]
S29GL032M11FFIS3@FBGA64 [DX5004]
S29GL032M11FFIS4@FBGA64 [DX5004]
S29GL032M11TAIR0@FBGA48 [DX1006]
S29GL032M11TAIR1@TSOP56 [DX1011]
S29GL032M11TAIR2@TSOP56 [DX1011]
S29GL032M11TAIR3@TSOP48 [DX1004]
S29GL032M11TAIR4@TSOP48 [DX1004]
S29GL032M11TBIR3@TSOP48 [DX1004]
S29GL032M11TBIR4@TSOP48 [DX1004]
S29GL032M11TCIR3@TSOP48 [DX1004]
S29GL032M11TCIR4@TSOP48 [DX1004]
S29GL032M11TFIR0@FBGA48 [DX1006]
S29GL032M11TFIR1@TSOP56 [DX1011]
S29GL032M11TFIR2@TSOP56 [DX1011]
S29GL032M11TFIR3@TSOP48 [DX1004]
S29GL032M11TFIR4@TSOP48 [DX1004]

S29GL032M90BACR0@FBGA48 [DX5022]
S29GL032M90BACR3@FBGA48 [DX5022]
S29GL032M90BACR4@FBGA48 [DX5022]
S29GL032M90BAIR0@FBGA48 [DX5022]
S29GL032M90BAIR3@FBGA48 [DX5022]
S29GL032M90BAIR4@FBGA48 [DX5022]
S29GL032M90BAIR5@FBGA48 [DX5002]
S29GL032M90BAIR6@FBGA48 [DX5002]
S29GL032M90BFCR0@FBGA48 [DX5022]
S29GL032M90BFCR3@FBGA48 [DX5022]
S29GL032M90BFCR4@FBGA48 [DX5022]
S29GL032M90BFIR0@FBGA48 [DX5022]
S29GL032M90BFIR3@FBGA48 [DX5022]
S29GL032M90BFIR4@FBGA48 [DX5022]
S29GL032M90BFIR5@FBGA48 [DX5002]
S29GL032M90BFIR6@FBGA48 [DX5002]
S29GL032M90FACR1@FBGA64 [DX5074]
S29GL032M90FACR2@FBGA64 [DX5074]
S29GL032M90FACR3@FBGA64 [DX5074]
S29GL032M90FACR4@FBGA64 [DX5074]
S29GL032M90FAIR1@FBGA64 [DX5074]
S29GL032M90FAIR2@FBGA64 [DX5074]
S29GL032M90FAIR3@FBGA64 [DX5074]
S29GL032M90FAIR4@FBGA64 [DX5074]
S29GL032M90FFCR1@FBGA64 [DX5074]
S29GL032M90FFCR2@FBGA64 [DX5074]
S29GL032M90FFCR3@FBGA64 [DX5074]
S29GL032M90FFCR4@FBGA64 [DX5074]
S29GL032M90FFIR1@FBGA64 [DX5074]
S29GL032M90FFIR2@FBGA64 [DX5074]
S29GL032M90FFIR3@FBGA64 [DX5074]
S29GL032M90FFIR4@FBGA64 [DX5074]
S29GL032M90TACR0@TSOP40 [DX1006]
S29GL032M90TACR1@TSOP56 [DX1011]
S29GL032M90TACR2@TSOP56 [DX1011]
S29GL032M90TACR3@TSOP48 [DX1004]
S29GL032M90TACR4@TSOP48 [DX1004]
S29GL032M90TAIR0@TSOP40 [DX1006]
S29GL032M90TAIR1@TSOP56 [DX1011]
S29GL032M90TAIR2@TSOP56 [DX1011]
S29GL032M90TAIR3@TSOP48 [DX1004]
S29GL032M90TAIR4@TSOP48 [DX1004]
S29GL032M90TBIR3@TSOP48 [DX1004]
S29GL032M90TBIR4@TSOP48 [DX1004]
S29GL032M90TCIR3@TSOP48 [DX1004]
S29GL032M90TCIR4@TSOP48 [DX1004]
S29GL032M90TFCR0@TSOP40 [DX1006]
S29GL032M90TFCR1@TSOP56 [DX1011]
S29GL032M90TFCR2@TSOP56 [DX1011]
S29GL032M90TFCR3@TSOP48 [DX1004]
S29GL032M90TFCR4@TSOP48 [DX1004]
S29GL032M90TFIR0@TSOP40 [DX1006]
S29GL032M90TFIR1@TSOP56 [DX1011]
S29GL032M90TFIR2@TSOP56 [DX1011]
S29GL032M90TFIR3@TSOP48 [DX1004]
S29GL032M90TFIR4@TSOP48 [DX1004]
S29GL032N11DAIV1@FBGA64 [DX5103]
S29GL032N11DAIV2@FBGA64 [DX5103]
S29GL032N11DFIV1@FBGA64 [DX5103]
S29GL032N11DFIV2@FBGA64 [DX5103]
S29GL032N11FAIS1@FBGA64 [DX5074]
S29GL032N11FAIS2@FBGA64 [DX5074]
S29GL032N11FAIS3@FBGA64 [DX5004]
S29GL032N11FAIS4@FBGA64 [DX5004]
S29GL032N11FAIV1@GBGA64 [DX5074]
S29GL032N11FAIV2@GBGA64 [DX5074]
S29GL032N11FFIS1@FBGA64 [DX5074]
S29GL032N11FFIS2@FBGA64 [DX5074]
S29GL032N11FFIS3@FBGA64 [DX5004]
S29GL032N11FFIS4@FBGA64 [DX5004]
S29GL032N11FFIV1@FBGA64 [DX5074]
S29GL032N11FFIV2@FBGA64 [DX5074]
S29GL032N11TAIV1@TSOP56 [DX1011]
S29GL032N11TAIV2@TSOP56 [DX1011]
S29GL032N11TFIV1@TSOP56 [DX1011]
S29GL032N11TFIV2@TSOP56 [DX1011]
S29GL032N70BAI03@FBGA48 [DX5043]
S29GL032N70BAI04@FBGA48 [DX5043]
S29GL032N70BAIR3@FBGA48 [DX5043]
S29GL032N70BAIR4@FBGA48 [DX5043]
S29GL032N70BFI03@FBGA48 [DX5043]
S29GL032N70BFI04@FBGA48 [DX5043]
S29GL032N70BFIR3@FBGA48 [DX5043]
S29GL032N70BFIR4@FBGA48 [DX5043]
S29GL032N70FAI01@FBGA64 [DX5074]
S29GL032N70FAI02@FBGA64 [DX5074]
S29GL032N70FAI03@FBGA64 [DX5074]
S29GL032N70FAI04@FBGA64 [DX5074]
S29GL032N70FAIR1@FBGA64 [DX5074]
S29GL032N70FAIR2@FBGA64 [DX5074]
S29GL032N70FAIR3@FBGA64 [DX5074]
S29GL032N70FAIR4@FBGA64 [DX5074]
S29GL032N70FFI01@FBGA64 [DX5074]
S29GL032N70FFI02@FBGA64 [DX5074]
S29GL032N70FFI03@FBGA64 [DX5074]
S29GL032N70FFI04@FBGA64 [DX5074]

S29GL032N70FFIR1@FBGA64 [DX5074] S29GL032N70FFIR2@FBGA64 [DX5074]
S29GL032N70FFIR3@FBGA64 [DX5074] S29GL032N70FFIR4@FBGA64 [DX5074]
S29GL032N70TAI01@TSOP56 [DX1011] S29GL032N70TAI02@TSOP56 [DX1011]
S29GL032N70TAI03@TSOP48 [DX1004] S29GL032N70TAI04@TSOP48 [DX1004]
S29GL032N70TAIR1@TSOP56 [DX1011] S29GL032N70TAIR2@TSOP56 [DX1011]
S29GL032N70TAIR3@TSOP48 [DX1004] S29GL032N70TAIR4@TSOP48 [DX1004]
S29GL032N70TFI01@TSOP56 [DX1011] S29GL032N70TFI02@TSOP56 [DX1011]
S29GL032N70TFI03@TSOP48 [DX1004] S29GL032N70TFI04@TSOP48 [DX1004]
S29GL032N70TFIR1@TSOP56 [DX1011] S29GL032N70TFIR2@TSOP56 [DX1011]
S29GL032N70TFIR3@TSOP48 [DX1004] S29GL032N70TFIR4@TSOP48 [DX1004]
S29GL032N90BAI03@FBGA48 [DX5043] S29GL032N90BAI04@FBGA48 [DX5043]
S29GL032N90BAIR3@FBGA48 [DX5043] S29GL032N90BAIR4@FBGA48 [DX5043]
S29GL032N90BFI03@FBGA48 [DX5043] S29GL032N90BFI04@FBGA48 [DX5043]
S29GL032N90BFIR3@FBGA48 [DX5043] S29GL032N90BFIR4@FBGA48 [DX5043]
S29GL032N90DAI01@FBGA64 [DX5103] S29GL032N90DAI02@FBGA64 [DX5103]
S29GL032N90DAI03@FBGA64 [DX5103] S29GL032N90DAI04@FBGA64 [DX5103]
S29GL032N90DFI01@FBGA64 [DX5103] S29GL032N90DFI02@FBGA64 [DX5103]
S29GL032N90DFI03@FBGA64 [DX5103] S29GL032N90DFI04@FBGA64 [DX5103]
S29GL032N90FAI01@FBGA64 [DX5074] S29GL032N90FAI02@FBGA64 [DX5074]
S29GL032N90FAI03@FBGA64 [DX5074] S29GL032N90FAI04@FBGA64 [DX5074]
S29GL032N90FAIR1@FBGA64 [DX5074] S29GL032N90FAIR2@FBGA64 [DX5074]
S29GL032N90FAIR3@FBGA64 [DX5074] S29GL032N90FAIR4@FBGA64 [DX5074]
S29GL032N90FAIS1@FBGA64 [DX5074] S29GL032N90FAIS2@FBGA64 [DX5074]
S29GL032N90FAIS3@FBGA64 [DX5004] S29GL032N90FAIS4@FBGA64 [DX5004]
S29GL032N90FAIV1@FBGA64 [DX5074] S29GL032N90FAIV2@FBGA64 [DX5074]
S29GL032N90FFI01@FBGA64 [DX5074] S29GL032N90FFI02@FBGA64 [DX5074]
S29GL032N90FFI03@FBGA64 [DX5074] S29GL032N90FFI04@FBGA64 [DX5074]
S29GL032N90FFIR1@FBGA64 [DX5074] S29GL032N90FFIR2@FBGA64 [DX5074]
S29GL032N90FFIR3@FBGA64 [DX5074] S29GL032N90FFIR4@FBGA64 [DX5074]
S29GL032N90FFIS1@FBGA64 [DX5074] S29GL032N90FFIS2@FBGA64 [DX5074]
S29GL032N90FFIS3(HS)@FBGA64 [DX5004]
S29GL032N90FFIS3@FBGA64 [DX5004] S29GL032N90FFIS4@FBGA64 [DX5004]
S29GL032N90FFIV1@FBGA64 [DX5074] S29GL032N90FFIV2@FBGA64 [DX5074]
S29GL032N90TAI01@TSOP56 [DX1011] S29GL032N90TAI02@TSOP56 [DX1011]
S29GL032N90TAI03@TSOP48 [DX1004] S29GL032N90TAI04@TSOP48 [DX1004]
S29GL032N90TAIR1@TSOP56 [DX1011] S29GL032N90TAIR2@TSOP56 [DX1011]
S29GL032N90TAIR3@TSOP48 [DX1004] S29GL032N90TAIR4@TSOP48 [DX1004]
S29GL032N90TAIV1@TSOP56 [DX1011] S29GL032N90TAIV2@TSOP56 [DX1011]
S29GL032N90TFI01@TSOP56 [DX1011] S29GL032N90TFI02@TSOP56 [DX1011]
S29GL032N90TFI03@TSOP48 [DX1004] S29GL032N90TFI04@TSOP48 [DX1004]
S29GL032N90TFIR1@TSOP56 [DX1011] S29GL032N90TFIR2@TSOP56 [DX1011]
S29GL032N90TFIR3@TSOP48 [DX1004] S29GL032N90TFIR4@TSOP48 [DX1004]
S29GL032N90TFIV1@TSOP56 [DX1011] S29GL032N90TFIV2@TSOP56 [DX1011]
S29GL064A10BAIR3@FBGA48 [DX5083] S29GL064A10BAIR4@FBGA48 [DX5083]
S29GL064A10BAIR5@FBGA48 [DX5083] S29GL064A10BFIR3@FBGA48 [DX5083]
S29GL064A10BFIR4@FBGA48 [DX5083] S29GL064A10BFIR5@FBGA48 [DX5083]
S29GL064A10FAIR1@FBGA64 [DX5074] S29GL064A10FAIR2@FBGA64 [DX5074]
S29GL064A10FAIR3@FBGA64 [DX5074] S29GL064A10FAIR4@FBGA64 [DX5074]

S29GL064A10FAIR5@FBGA64 [DX5074] S29GL064A10FFIR1@FBGA64 [DX5074]
S29GL064A10FFIR2@FBGA64 [DX5074] S29GL064A10FFIR3@FBGA64 [DX5074]
S29GL064A10FFIR4@FBGA64 [DX5074] S29GL064A10FFIR5@FBGA64 [DX5074]
S29GL064A10TAIR1@TSOP56 [DX1011] S29GL064A10TAIR2@TSOP56 [DX1011]
S29GL064A10TAIR3@TSOP48 [DX1004] S29GL064A10TAIR4@TSOP48 [DX1004]
S29GL064A10TAIR6@TSOP48 [DX1004] S29GL064A10TAIR7@TSOP48 [DX1004]
S29GL064A10TAIR8@TSOP48 [DX1004] S29GL064A10TAIR9@TSOP48 [DX1004]
S29GL064A10TFIR1@TSOP56 [DX1011] S29GL064A10TFIR2@TSOP56 [DX1011]
S29GL064A10TFIR3@TSOP48 [DX1004] S29GL064A10TFIR4@TSOP48 [DX1004]
S29GL064A10TFIR6@TSOP48 [DX1004] S29GL064A10TFIR7@TSOP48 [DX1004]
S29GL064A10TFIR8@TSOP48 [DX1004] S29GL064A10TFIR9@TSOP48 [DX1004]
S29GL064A11BAIR3@FBGA48 [DX5083] S29GL064A11BAIR4@FBGA48 [DX5083]
S29GL064A11BAIR5@FBGA48 [DX5083] S29GL064A11BFIR3@FBGA48 [DX5083]
S29GL064A11BFIR4@FBGA48 [DX5083] S29GL064A11BFIR5@FBGA48 [DX5083]
S29GL064A11FAIR1@FBGA64 [DX5074] S29GL064A11FAIR2@FBGA64 [DX5074]
S29GL064A11FAIR3@FBGA64 [DX5074] S29GL064A11FAIR4@FBGA64 [DX5074]
S29GL064A11FAIR5@FBGA64 [DX5074] S29GL064A11FAIS1@FBGA64 [DX5074]
S29GL064A11FAIS2@FBGA64 [DX5074] S29GL064A11FAIS3@FBGA64 [DX5004]
S29GL064A11FAIS4@FBGA64 [DX5004] S29GL064A11FFIR1@FBGA64 [DX5074]
S29GL064A11FFIR2@FBGA64 [DX5074] S29GL064A11FFIR3@FBGA64 [DX5074]
S29GL064A11FFIR4@FBGA64 [DX5074] S29GL064A11FFIR5@FBGA64 [DX5074]
S29GL064A11FFIS1@FBGA64 [DX5074] S29GL064A11FFIS2@FBGA64 [DX5074]
S29GL064A11FFIS3@FBGA64 [DX5004] S29GL064A11FFIS4@FBGA64 [DX5004]
S29GL064A11TAIR1@TSOP56 [DX1011] S29GL064A11TAIR2@TSOP56 [DX1011]
S29GL064A11TAIR3@TSOP48 [DX1004] S29GL064A11TAIR4@TSOP48 [DX1004]
S29GL064A11TAIR6@TSOP48 [DX1004] S29GL064A11TAIR7@TSOP48 [DX1004]
S29GL064A11TAIR8@TSOP48 [DX1004] S29GL064A11TAIR9@TSOP48 [DX1004]
S29GL064A11TFIR1@TSOP56 [DX1011] S29GL064A11TFIR2@TSOP56 [DX1011]
S29GL064A11TFIR3@TSOP48 [DX1004] S29GL064A11TFIR4@TSOP48 [DX1004]
S29GL064A11TFIR6@TSOP48 [DX1004] S29GL064A11TFIR7@TSOP48 [DX1004]
S29GL064A11TFIR8@TSOP48 [DX1004] S29GL064A11TFIR9@TSOP48 [DX1004]
S29GL064A90BAIR3@FBGA48 [DX5083] S29GL064A90BAIR4@FBGA48 [DX5083]
S29GL064A90BAIR5@FBGA48 [DX5083] S29GL064A90BFIR3@FBGA48 [DX5083]
S29GL064A90BFIR4@FBGA48 [DX5083] S29GL064A90BFIR5@FBGA48 [DX5083]
S29GL064A90FAIR1@FBGA64 [DX5074] S29GL064A90FAIR2@FBGA64 [DX5074]
S29GL064A90FAIR3@FBGA64 [DX5074] S29GL064A90FAIR4@FBGA64 [DX5074]
S29GL064A90FAIR5@FBGA64 [DX5074] S29GL064A90FAIS1@FBGA64 [DX5074]
S29GL064A90FAIS2@FBGA64 [DX5074] S29GL064A90FAIS3@FBGA64 [DX5004]
S29GL064A90FAIS4@FBGA64 [DX5004] S29GL064A90FFIR1@FBGA64 [DX5074]
S29GL064A90FFIR2@FBGA64 [DX5074] S29GL064A90FFIR3@FBGA64 [DX5074]
S29GL064A90FFIR4@FBGA64 [DX5074] S29GL064A90FFIR5@FBGA64 [DX5074]
S29GL064A90FFIS1@FBGA64 [DX5074] S29GL064A90FFIS2@FBGA64 [DX5074]
S29GL064A90FFIS3@FBGA64 [DX5004] S29GL064A90FFIS4@FBGA64 [DX5004]
S29GL064A90TAIR1@TSOP56 [DX1011] S29GL064A90TAIR2@TSOP56 [DX1011]
S29GL064A90TAIR3@TSOP48 [DX1004] S29GL064A90TAIR4@TSOP48 [DX1004]
S29GL064A90TAIR6@TSOP48 [DX1004] S29GL064A90TAIR7@TSOP48 [DX1004]
S29GL064A90TAIR8@TSOP48 [DX1004] S29GL064A90TAIR9@TSOP48 [DX1004]
S29GL064A90TFIR1@TSOP56 [DX1011] S29GL064A90TFIR2@TSOP56 [DX1011]

S29GL064A90TFIR3@TSOP48 [DX1004]
S29GL064A90TFIR4@TSOP48 [DX1004]
S29GL064A90TFIR6@TSOP48 [DX1004]
S29GL064A90TFIR7@TSOP48 [DX1004]
S29GL064A90TFIR8@TSOP48 [DX1004]
S29GL064A90TFIR9@TSOP48 [DX1004]
S29GL064AS4@SSOP56 [DX0051]
S29GL064M10BAIR0@FBGA63 [DX5041]
S29GL064M10BAIR3@FBGA63 [DX5041]
S29GL064M10BAIR4@FBGA63 [DX5041]
S29GL064M10BAIR5@FBGA63 [DX5041]
S29GL064M10BFIR0@FBGA63 [DX5041]
S29GL064M10BFIR3@FBGA63 [DX5041]
S29GL064M10BFIR4@FBGA63 [DX5041]
S29GL064M10BFIR5@FBGA63 [DX5041]
S29GL064M10FAIR1@FBGA64 [DX5074]
S29GL064M10FAIR2@FBGA64 [DX5074]
S29GL064M10FAIR3@FBGA64 [DX5074]
S29GL064M10FAIR4@FBGA64 [DX5074]
S29GL064M10FAIR5@FBGA64 [DX5074]
S29GL064M10FFIR1@FBGA64 [DX5074]
S29GL064M10FFIR2@FBGA64 [DX5074]
S29GL064M10FFIR3@FBGA64 [DX5074]
S29GL064M10FFIR4@FBGA64 [DX5074]
S29GL064M10FFIR5@FBGA64 [DX5074]
S29GL064M10TAIR0@FBGA63 [DX1004]
S29GL064M10TAIR1@TSOP56 [DX1011]
S29GL064M10TAIR2@TSOP56 [DX1011]
S29GL064M10TAIR3@TSOP48 [DX1004]
S29GL064M10TAIR4@TSOP48 [DX1004]
S29GL064M10TAIR6@TSOP48 [DX1004]
S29GL064M10TAIR7@TSOP48 [DX1004]
S29GL064M10TAIR8@TSOP56 [DX1011]
S29GL064M10TAIR9@TSOP56 [DX1011]
S29GL064M10TBIR6@TSOP48 [DX1004]
S29GL064M10TBIR7@TSOP48 [DX1004]
S29GL064M10TCIR6@TSOP48 [DX1004]
S29GL064M10TCIR7@TSOP48 [DX1004]
S29GL064M10TDIR8@TSOP56 [DX1011]
S29GL064M10TDIR9@TSOP56 [DX1011]
S29GL064M10TFIR0@FBGA63 [DX1004]
S29GL064M10TFIR1@TSOP56 [DX1011]
S29GL064M10TFIR2@TSOP56 [DX1011]
S29GL064M10TFIR3@TSOP48 [DX1004]
S29GL064M10TFIR4@TSOP48 [DX1004]
S29GL064M10TFIR6@TSOP48 [DX1004]
S29GL064M10TFIR7@TSOP48 [DX1004]
S29GL064M11BAIR0@FBGA63 [DX5041]
S29GL064M11BAIR3@FBGA63 [DX5041]
S29GL064M11BAIR4@FBGA63 [DX5041]
S29GL064M11BAIR5@FBGA63 [DX5041]
S29GL064M11BFIR0@FBGA63 [DX5041]
S29GL064M11BFIR3@FBGA63 [DX5041]
S29GL064M11BFIR4@FBGA63 [DX5041]
S29GL064M11BFIR5@FBGA63 [DX5041]
S29GL064M11FAIR1@FBGA64 [DX5074]
S29GL064M11FAIR2@FBGA64 [DX5074]
S29GL064M11FAIR3@FBGA64 [DX5074]
S29GL064M11FAIR4@FBGA64 [DX5074]
S29GL064M11FAIR5@FBGA64 [DX5074]
S29GL064M11FAIS1@FBGA64 [DX5074]
S29GL064M11FAIS2@FBGA64 [DX5074]
S29GL064M11FAIS3@FBGA64 [DX5004]
S29GL064M11FAIS4@FBGA64 [DX5004]
S29GL064M11FFIR1@FBGA64 [DX5074]
S29GL064M11FFIR2@FBGA64 [DX5074]
S29GL064M11FFIR3@FBGA64 [DX5074]
S29GL064M11FFIR4@FBGA64 [DX5074]
S29GL064M11FFIR5@FBGA64 [DX5074]
S29GL064M11FFIS1@FBGA64 [DX5074]
S29GL064M11FFIS2@FBGA64 [DX5074]
S29GL064M11FFIS3@FBGA64 [DX5004]
S29GL064M11FFIS4@FBGA64 [DX5004]
S29GL064M11TAIR0@FBGA63 [DX1004]
S29GL064M11TAIR1@TSOP56 [DX1011]
S29GL064M11TAIR2@TSOP56 [DX1011]
S29GL064M11TAIR3@TSOP48 [DX1004]
S29GL064M11TAIR4@TSOP48 [DX1004]
S29GL064M11TAIR6@TSOP48 [DX1004]
S29GL064M11TAIR7@TSOP48 [DX1004]
S29GL064M11TAIR8@TSOP56 [DX1011]
S29GL064M11TAIR9@TSOP56 [DX1011]
S29GL064M11TBIR6@TSOP48 [DX1004]
S29GL064M11TBIR7@TSOP48 [DX1004]
S29GL064M11TCIR6@TSOP48 [DX1004]
S29GL064M11TCIR7@TSOP48 [DX1004]
S29GL064M11TDIR8@TSOP56 [DX1011]
S29GL064M11TDIR9@TSOP56 [DX1011]
S29GL064M11TFIR0@FBGA63 [DX1004]
S29GL064M11TFIR1@TSOP56 [DX1011]
S29GL064M11TFIR2@TSOP56 [DX1011]
S29GL064M11TFIR3@TSOP48 [DX1004]
S29GL064M11TFIR4@TSOP48 [DX1004]
S29GL064M11TFIR6@TSOP48 [DX1004]
S29GL064M11TFIR7@TSOP48 [DX1004]
S29GL064M90BAIR0@FBGA63 [DX5041]

S29GL064M90BAIR3@FBGA63 [DX5041]　　S29GL064M90BAIR4@FBGA63 [DX5041]
S29GL064M90BAIR5@FBGA63 [DX5041]　　S29GL064M90BFIR0@FBGA63 [DX5041]
S29GL064M90BFIR3@FBGA63 [DX5041]　　S29GL064M90BFIR4@FBGA63 [DX5041]
S29GL064M90BFIR5@FBGA63 [DX5041]　　S29GL064M90FAIR1@FBGA64 [DX5074]
S29GL064M90FAIR2@FBGA64 [DX5074]　　S29GL064M90FAIR3@FBGA64 [DX5074]
S29GL064M90FAIR4@FBGA64 [DX5074]　　S29GL064M90FAIR5@FBGA64 [DX5074]
S29GL064M90FFIR1@FBGA64 [DX5074]　　S29GL064M90FFIR2@FBGA64 [DX5074]
S29GL064M90FFIR3@FBGA64 [DX5074]　　S29GL064M90FFIR4@FBGA64 [DX5074]
S29GL064M90FFIR5@FBGA64 [DX5074]　　S29GL064M90TAIR0@TSOP48 [DX1004]
S29GL064M90TAIR1@TSOP56 [DX1011]　　S29GL064M90TAIR2@TSOP56 [DX1011]
S29GL064M90TAIR3@TSOP48 [DX1004]　　S29GL064M90TAIR4@TSOP48 [DX1004]
S29GL064M90TAIR6@TSOP48 [DX1004]　　S29GL064M90TAIR7@TSOP48 [DX1004]
S29GL064M90TAIR8@TSOP56 [DX1011]　　S29GL064M90TAIR9@TSOP56 [DX1011]
S29GL064M90TBIR6@TSOP48 [DX1004]　　S29GL064M90TBIR7@TSOP48 [DX1004]
S29GL064M90TCIR6@TSOP48 [DX1004]　　S29GL064M90TCIR7@TSOP48 [DX1004]
S29GL064M90TDIR8@TSOP56 [DX1011]　　S29GL064M90TDIR9@TSOP56 [DX1011]
S29GL064M90TFIR0@TSOP48 [DX1004]　　S29GL064M90TFIR1@TSOP56 [DX1011]
S29GL064M90TFIR2@TSOP56 [DX1011]　　S29GL064M90TFIR3@TSOP48 [DX1004]
S29GL064M90TFIR4@TSOP48 [DX1004]　　S29GL064M90TFIR6@TSOP48 [DX1004]
S29GL064M90TFIR7@TSOP48 [DX1004]　　S29GL064N11DAIV1@FBGA64 [DX5103]
S29GL064N11DAIV2@FBGA64 [DX5103]　　S29GL064N11DFIV1@FBGA64 [DX5103]
S29GL064N11DFIV2@FBGA64 [DX5103]　　S29GL064N11FAIS1@FBGA64 [DX5074]
S29GL064N11FAIS2@FBGA64 [DX5074]
S29GL064N11FAIS3(HD)@FBGA64 [DX5004]
S29GL064N11FAIS3@FBGA64 [DX5004]　　S29GL064N11FAIS4@FBGA64 [DX5004]
S29GL064N11FAIV1@FBGA64 [DX5074]　　S29GL064N11FAIV2@FBGA64 [DX5074]
S29GL064N11FFIS1@FBGA64 [DX5074]　　S29GL064N11FFIS2@FBGA64 [DX5074]
S29GL064N11FFIS3(HD)@FBGA64 [DX5004]
S29GL064N11FFIS3@FBGA64 [DX5004]　　S29GL064N11FFIS4@FBGA64 [DX5004]
S29GL064N11FFIV1@FBGA64 [DX5074]　　S29GL064N11FFIV2@FBGA64 [DX5074]
S29GL064N11TAIV1@TSOP56 [DX1011]　　S29GL064N11TAIV2@TSOP56 [DX1011]
S29GL064N11TAIV6@TSOP48 [DX1004]　　S29GL064N11TAIV7@TSOP48 [DX1004]
S29GL064N11TFIV1@TSOP56 [DX1011]　　S29GL064N11TFIV2@TSOP56 [DX1011]
S29GL064N11TFIV6@TSOP48 [DX1004]　　S29GL064N11TFIV7@TSOP48 [DX1004]
S29GL064N70BAI03@FBGA48 [DX5043]　　S29GL064N70BAI04@FBGA48 [DX5043]
S29GL064N70BAIR3@FBGA48 [DX5043]　　S29GL064N70BAIR4@FBGA48 [DX5043]
S29GL064N70BFI03@FBGA48 [DX5043]　　S29GL064N70BFI04@FBGA48 [DX5043]
S29GL064N70BFIR3@FBGA48 [DX5043]　　S29GL064N70BFIR4@FBGA48 [DX5043]
S29GL064N70FAI01@FBGA64 [DX5074]　　S29GL064N70FAI02@FBGA64 [DX5074]
S29GL064N70FAI03@FBGA64 [DX5074]　　S29GL064N70FAI04@FBGA64 [DX5074]
S29GL064N70FAIR1@FBGA64 [DX5074]　　S29GL064N70FAIR2@FBGA64 [DX5074]
S29GL064N70FAIR3@FBGA64 [DX5074]　　S29GL064N70FAIR4@FBGA64 [DX5074]
S29GL064N70FFI01@FBGA64 [DX5074]　　S29GL064N70FFI02@FBGA64 [DX5074]
S29GL064N70FFI03@FBGA64 [DX5074]　　S29GL064N70FFI04@FBGA64 [DX5074]
S29GL064N70FFIR1@FBGA64 [DX5074]　　S29GL064N70FFIR2@FBGA64 [DX5074]
S29GL064N70FFIR3@FBGA64 [DX5074]　　S29GL064N70FFIR4@FBGA64 [DX5074]
S29GL064N70TAI01@TSOP56 [DX1011]　　S29GL064N70TAI02@TSOP56 [DX1011]
S29GL064N70TAI03@TSOP48 [DX1004]　　S29GL064N70TAI04@TSOP48 [DX1004]

S29GL064N70TAI06@TSOP48 [DX1004] S29GL064N70TAI07@TSOP48 [DX1004]
S29GL064N70TAIR1@TSOP56 [DX1011] S29GL064N70TAIR2@TSOP56 [DX1011]
S29GL064N70TAIR3@TSOP48 [DX1004] S29GL064N70TAIR4@TSOP48 [DX1004]
S29GL064N70TAIR6@TSOP48 [DX1004] S29GL064N70TAIR7@TSOP48 [DX1004]
S29GL064N70TFI01@TSOP56 [DX1011] S29GL064N70TFI02@TSOP56 [DX1011]
S29GL064N70TFI03@TSOP48 [DX1004] S29GL064N70TFI04@TSOP48 [DX1004]
S29GL064N70TFI06@TSOP48 [DX1004] S29GL064N70TFI07@TSOP48 [DX1004]
S29GL064N70TFIR1@TSOP56 [DX1011] S29GL064N70TFIR2@TSOP56 [DX1011]
S29GL064N70TFIR3@TSOP48 [DX1004] S29GL064N70TFIR4@TSOP48 [DX1004]
S29GL064N70TFIR6@TSOP48 [DX1004] S29GL064N70TFIR7@TSOP48 [DX1004]
S29GL064N90BAI03@FBGA48 [DX5043] S29GL064N90BAI04@FBGA48 [DX5043]
S29GL064N90BAIR3@FBGA48 [DX5043] S29GL064N90BAIR4@FBGA48 [DX5043]
S29GL064N90BFI03@FBGA48 [DX5043] S29GL064N90BFI04@FBGA48 [DX5043]
S29GL064N90BFIR3@FBGA48 [DX5043] S29GL064N90BFIR4@FBGA48 [DX5043]
S29GL064N90DAI01@FBGA64 [DX5103] S29GL064N90DAI02@FBGA64 [DX5103]
S29GL064N90DAI03@FBGA64 [DX5103] S29GL064N90DAI04@FBGA64 [DX5103]
S29GL064N90DFI01@FBGA64 [DX5103] S29GL064N90DFI02@FBGA64 [DX5103]
S29GL064N90DFI03@FBGA64 [DX5103] S29GL064N90DFI04@FBGA64 [DX5103]
S29GL064N90FAI01@FBGA64 [DX5074] S29GL064N90FAI02@FBGA64 [DX5074]
S29GL064N90FAI03@FBGA64 [DX5074] S29GL064N90FAI04@FBGA64 [DX5074]
S29GL064N90FAIR1@FBGA64 [DX5074] S29GL064N90FAIR2@FBGA64 [DX5074]
S29GL064N90FAIR3@FBGA64 [DX5074] S29GL064N90FAIR4@FBGA64 [DX5074]
S29GL064N90FAIS1@FBGA64 [DX5074] S29GL064N90FAIS2@FBGA64 [DX5074]
S29GL064N90FAIS3(HD)@FBGA64 [DX5004]
S29GL064N90FAIS3@FBGA64 [DX5004] S29GL064N90FAIS4@FBGA64 [DX5004]
S29GL064N90FAIV1@FBGA64 [DX5074] S29GL064N90FAIV2@FBGA64 [DX5074]
S29GL064N90FFI01@FBGA64 [DX5074] S29GL064N90FFI02@FBGA64 [DX5074]
S29GL064N90FFI03@FBGA64 [DX5074] S29GL064N90FFI04@FBGA64 [DX5074]
S29GL064N90FFIR1@FBGA64 [DX5074] S29GL064N90FFIR2@FBGA64 [DX5074]
S29GL064N90FFIR3@FBGA64 [DX5074] S29GL064N90FFIR4@FBGA64 [DX5074]
S29GL064N90FFIS1@FBGA64 [DX5074] S29GL064N90FFIS2@FBGA64 [DX5074]
S29GL064N90FFIS3(HD)@FBGA64 [DX5004]
S29GL064N90FFIS3@FBGA64 [DX5004] S29GL064N90FFIS4@FBGA64 [DX5004]
S29GL064N90FFIV1@FBGA64 [DX5074] S29GL064N90FFIV2@FBGA64 [DX5074]
S29GL064N90TAI01@TSOP56 [DX1011] S29GL064N90TAI02@TSOP56 [DX1011]
S29GL064N90TAI03@TSOP48 [DX1004] S29GL064N90TAI04@TSOP48 [DX1004]
S29GL064N90TAI06@TSOP48 [DX1004] S29GL064N90TAI07@TSOP48 [DX1004]
S29GL064N90TAIR1@TSOP56 [DX1011] S29GL064N90TAIR2@TSOP56 [DX1011]
S29GL064N90TAIR3@TSOP48 [DX1004] S29GL064N90TAIR4@TSOP48 [DX1004]
S29GL064N90TAIR6@TSOP48 [DX1004] S29GL064N90TAIR7@TSOP48 [DX1004]
S29GL064N90TAIV1@TSOP56 [DX1011] S29GL064N90TAIV2@TSOP56 [DX1011]
S29GL064N90TAIV6@TSOP48 [DX1004] S29GL064N90TAIV7@TSOP48 [DX1004]
S29GL064N90TFI01@TSOP56 [DX1011] S29GL064N90TFI02@TSOP56 [DX1011]
S29GL064N90TFI03@TSOP48 [DX1004] S29GL064N90TFI04@TSOP48 [DX1004]
S29GL064N90TFI06@TSOP48 [DX1004] S29GL064N90TFI07@TSOP48 [DX1004]
S29GL064N90TFIR1@TSOP56 [DX1011] S29GL064N90TFIR2@TSOP56 [DX1011]
S29GL064N90TFIR3@TSOP48 [DX1004] S29GL064N90TFIR4@TSOP48 [DX1004]
S29GL064N90TFIR6@TSOP48 [DX1004] S29GL064N90TFIR7@TSOP48 [DX1004]

S29GL064N90TFIV1@TSOP56 [DX1011]
S29GL064N90TFIV2@TSOP56 [DX1011]
S29GL064N90TFIV6@TSOP48 [DX1004]
S29GL064N90TFIV7@TSOP48 [DX1004]
S29GL064S70BHI03@FBGA48 [DX5043]
S29GL064S70BHI04@FBGA48 [DX5043]
S29GL064S70DHI01@FBGA64 [DX5103]
S29GL064S70DHI02@FBGA64 [DX5103]
S29GL064S70DHI03@FBGA64 [DX5103]
S29GL064S70DHI04@FBGA64 [DX5103]
S29GL064S70FHI01@FBGA64 [DX5074]
S29GL064S70FHI02@FBGA64 [DX5074]
S29GL064S70FHI03@FBGA64 [DX5074]
S29GL064S70FHI04@FBGA64 [DX5074]
S29GL064S70TFI01@TSOP56 [DX1011]
S29GL064S70TFI02@TSOP56 [DX1011]
S29GL064S70TFI03@TSOP48 [DX1004]
S29GL064S70TFI04@TSOP48 [DX1004]
S29GL064S70TFI06@TSOP48 [DX1004]
S29GL064S70TFI07@TSOP48 [DX1004]
S29GL064S80BHV03@FBGA48 [DX5043]
S29GL064S80BHV04@FBGA48 [DX5043]
S29GL064S80DHIV1@FBGA64 [DX5103]
S29GL064S80DHIV2@FBGA64 [DX5103]
S29GL064S80DHV01@FBGA64 [DX5103]
S29GL064S80DHV02@FBGA64 [DX5103]
S29GL064S80DHV03@FBGA64 [DX5103]
S29GL064S80DHV04@FBGA64 [DX5103]
S29GL064S80FHIV1@FBGA64 [DX5074]
S29GL064S80FHIV2@FBGA64 [DX5074]
S29GL064S80FHV01@FBGA64 [DX5074]
S29GL064S80FHV02@FBGA64 [DX5074]
S29GL064S80FHV03@FBGA64 [DX5074]
S29GL064S80FHV04@FBGA64 [DX5074]
S29GL064S80TFIV1@TSOP56 [DX1011]
S29GL064S80TFIV2@TSOP56 [DX1011]
S29GL064S80TFIV6@TSOP48 [DX1004]
S29GL064S80TFIV7@TSOP48 [DX1004]
S29GL064S80TFV01@TSOP56 [DX1011]
S29GL064S80TFV02@TSOP56 [DX1011]
S29GL064S80TFV03@TSOP48 [DX1004]
S29GL064S80TFV04@TSOP48 [DX1004]
S29GL064S80TFV06@TSOP48 [DX1004]
S29GL064S80TFV07@TSOP48 [DX1004]
S29GL064S90DHVV1@FBGA64 [DX5103]
S29GL064S90DHVV2@FBGA64 [DX5103]
S29GL064S90FHVV1@FBGA64 [DX5074]
S29GL064S90FHVV2@FBGA64 [DX5074]
S29GL064S90TFVV1@TSOP56 [DX1011]
S29GL064S90TFVV2@TSOP56 [DX1011]
S29GL064S90TFVV6@TSOP48 [DX1004]
S29GL064S90TFVV7@TSOP48 [DX1004]
S29GL100GP@FBGA54 [DX5004]
S29GL128M10FAIR1@FBGA64 [DX5074]
S29GL128M10FAIR2@FBGA64 [DX5074]
S29GL128M10FFIR1@FBGA64 [DX5074]
S29GL128M10FFIR2@FBGA64 [DX5074]
S29GL128M10TAIR1@TSOP56 [DX1011]
S29GL128M10TAIR2@TSOP56 [DX1011]
S29GL128M10TAIR8@TSOP56 [DX1011]
S29GL128M10TAIR9@TSOP56 [DX1011]
S29GL128M10TDIR8@TSOP56 [DX1011]
S29GL128M10TDIR9@TSOP56 [DX1011]
S29GL128M10TFIR1@TSOP56 [DX1011]
S29GL128M10TFIR2@TSOP56 [DX1011]
S29GL128M11FAIR1@FBGA64 [DX5074]
S29GL128M11FAIR2@FBGA64 [DX5074]
S29GL128M11FFIR1@FBGA64 [DX5074]
S29GL128M11FFIR2@FBGA64 [DX5074]
S29GL128M11TAIR1@TSOP56 [DX1011]
S29GL128M11TAIR2@TSOP56 [DX1011]
S29GL128M11TAIR8@TSOP56 [DX1011]
S29GL128M11TAIR9@TSOP56 [DX1011]
S29GL128M11TDIR8@TSOP56 [DX1011]
S29GL128M11TDIR9@TSOP56 [DX1011]
S29GL128M11TFIR1@TSOP56 [DX1011]
S29GL128M11TFIR2@TSOP56 [DX1011]
S29GL128M90FAIR1@FBGA64 [DX5074]
S29GL128M90FAIR2@FBGA64 [DX5074]
S29GL128M90FFIR1@FBGA64 [DX5074]
S29GL128M90FFIR2@FBGA64 [DX5074]
S29GL128M90TAIR1@TSOP56 [DX1011]
S29GL128M90TAIR2@TSOP56 [DX1011]
S29GL128M90TAIR8@TSOP56 [DX1011]
S29GL128M90TAIR9@TSOP56 [DX1011]
S29GL128M90TDIR8@TSOP56 [DX1011]
S29GL128M90TDIR9@TSOP56 [DX1011]
S29GL128M90TFIR1@TSOP56 [DX1011]
S29GL128M90TFIR2@TSOP56 [DX1011]
S29GL128N10FAI01@FBGA64 [DX5074]
S29GL128N10FAI02@FBGA64 [DX5074]
S29GL128N10FAIS1@FBGA64 [DX5074]
S29GL128N10FAIS2@FBGA64 [DX5074]
S29GL128N10FAIS3@FBGA64 [DX5004]
S29GL128N10FAIS4@FBGA64 [DX5004]
S29GL128N10FFI01@FBGA64 [DX5074]

S29GL128N10FFI02@FBGA64 [DX5074]　　S29GL128N10FFIS1@FBGA64 [DX5074]
S29GL128N10FFIS2@FBGA64 [DX5074]　　S29GL128N10FFIS3@FBGA64 [DX5004]
S29GL128N10FFIS4@FBGA64 [DX5004]　　S29GL128N10TAI01@TSOP56 [DX1011]
S29GL128N10TAI02@TSOP56 [DX1011]　　S29GL128N10TFI01@TSOP56 [DX1011]
S29GL128N10TFI02@TSOP56 [DX1011]　　S29GL128N11FAI01@FBGA64 [DX5074]
S29GL128N11FAI02@FBGA64 [DX5074]　　S29GL128N11FAIIH@FBGA64 [DX5004]
S29GL128N11FAIS1@FBGA64 [DX5074]　　S29GL128N11FAIS2@FBGA64 [DX5074]
S29GL128N11FAIS3@FBGA64 [DX5004]　　S29GL128N11FAIS4@FBGA64 [DX5004]
S29GL128N11FAIV1@FBGA64 [DX5074]　　S29GL128N11FAIV2@FBGA64 [DX5074]
S29GL128N11FAW01@FBGA64 [DX5074]　　S29GL128N11FAW02@FBGA64 [DX5074]
S29GL128N11FAWIH@FBGA64 [DX5004]　　S29GL128N11FFI01@FBGA64 [DX5074]
S29GL128N11FFI02@FBGA64 [DX5074]　　S29GL128N11FFIIH@FBGA64 [DX5004]
S29GL128N11FFIS1@FBGA64 [DX5074]　　S29GL128N11FFIS2@FBGA64 [DX5074]
S29GL128N11FFIS3@FBGA64 [DX5004]　　S29GL128N11FFIS4@FBGA64 [DX5004]
S29GL128N11FFIV1@FBGA64 [DX5074]　　S29GL128N11FFIV2@FBGA64 [DX5074]
S29GL128N11FIW01@FBGA64 [DX5074]　　S29GL128N11FIW02@FBGA64 [DX5074]
S29GL128N11TAI01@TSOP56 [DX1011]　　S29GL128N11TAI02@TSOP56 [DX1011]
S29GL128N11TAIV1@TSOP56 [DX1011]　　S29GL128N11TAIV2@TSOP56 [DX1011]
S29GL128N11TAW01@TSOP56 [DX1011]　　S29GL128N11TAW02@TSOP56 [DX1011]
S29GL128N11TFI01@TSOP56 [DX1011]　　S29GL128N11TFI02@TSOP56 [DX1011]
S29GL128N11TFIV1@TSOP56 [DX1011]　　S29GL128N11TFIV2@TSOP56 [DX1011]
S29GL128N11TIW01@TSOP56 [DX1011]　　S29GL128N11TIW02@TSOP56 [DX1011]
S29GL128N90FAIR1@FBGA64 [DX5074]　　S29GL128N90FAIR2@FBGA64 [DX5074]
S29GL128N90FFIR1@FBGA64 [DX5074]　　S29GL128N90FFIR2@FBGA64 [DX5074]
S29GL128N90TAIR1@TSOP56 [DX1011]　　S29GL128N90TAIR2@TSOP56 [DX1011]
S29GL128N90TFIR1@TSOP56 [DX1011]　　S29GL128N90TFIR2@TSOP56 [DX1011]
S29GL128P10DAIS1@FBGA64 [DX5103]　　S29GL128P10DAIS2@FBGA64 [DX5103]
S29GL128P10DFIS1@FBGA64 [DX5103]　　S29GL128P10DFIS2@FBGA64 [DX5103]
S29GL128P10FAI01@FBGA64 [DX5074]　　S29GL128P10FAI02@FBGA64 [DX5074]
S29GL128P10FAIS1@FBGA64 [DX5074]　　S29GL128P10FAIS2@FBGA64 [DX5074]
S29GL128P10FAIS3@FBGA64 [DX5004]　　S29GL128P10FAIS4@FBGA64 [DX5004]
S29GL128P10FFI01@FBGA64 [DX5074]　　S29GL128P10FFI02@FBGA64 [DX5074]
S29GL128P10FFIS1@FBGA64 [DX5074]　　S29GL128P10FFIS2@FBGA64 [DX5074]
S29GL128P10FFIS3@FBGA64 [DX5004]　　S29GL128P10FFIS4@FBGA64 [DX5004]
S29GL128P10TAI01@TSOP56 [DX1011]　　S29GL128P10TAI02@TSOP56 [DX1011]
S29GL128P10TFI01(FH)@TSOP56 [DX1011]
S29GL128P10TFI01@TSOP56 [DX1011]　　S29GL128P10TFI02@TSOP56 [DX1011]
S29GL128P11DAIS1@FBGA64 [DX5103]　　S29GL128P11DAIS2@FBGA64 [DX5103]
S29GL128P11DAIS5@FBGA64 [DX5103]　　S29GL128P11DAIS6@FBGA64 [DX5103]
S29GL128P11DFIS1@FBGA64 [DX5103]　　S29GL128P11DFIS2@FBGA64 [DX5103]
S29GL128P11DFIS5@FBGA64 [DX5103]　　S29GL128P11DFIS6@FBGA64 [DX5103]
S29GL128P11FAI01@FBGA64 [DX5074]　　S29GL128P11FAI02@FBGA64 [DX5074]
S29GL128P11FAIS1@FBGA64 [DX5074]　　S29GL128P11FAIS2@FBGA64 [DX5074]
S29GL128P11FAIS3@FBGA64 [DX5004]　　S29GL128P11FAIS4@FBGA64 [DX5004]
S29GL128P11FAIS5@FBGA64 [DX5074]　　S29GL128P11FAIS6@FBGA64 [DX5074]
S29GL128P11FAIV1@FBGA64 [DX5074]　　S29GL128P11FAIV2@FBGA64 [DX5074]
S29GL128P11FFI01@FBGA64 [DX5074]　　S29GL128P11FFI02@FBGA64 [DX5074]
S29GL128P11FFIS1@FBGA64 [DX5074]　　S29GL128P11FFIS2@FBGA64 [DX5074]

S29GL128P11FFIS3@FBGA64 [DX5004]
S29GL128P11FFIS4@FBGA64 [DX5004]
S29GL128P11FFIS5@FBGA64 [DX5074]
S29GL128P11FFIS6@FBGA64 [DX5074]
S29GL128P11FFIV1@FBGA64 [DX5074]
S29GL128P11FFIV2@FBGA64 [DX5074]
S29GL128P11TAI01@TSOP56 [DX1011]
S29GL128P11TAI02@TSOP56 [DX1011]
S29GL128P11TAIV1@TSOP56 [DX1011]
S29GL128P11TAIV2@TSOP56 [DX1011]
S29GL128P11TFI01@TSOP56 [DX1011]
S29GL128P11TFI02@TSOP56 [DX1011]
S29GL128P11TFIV1@TSOP56 [DX1011]
S29GL128P11TFIV2@TSOP56 [DX1011]
S29GL128P90DAIS7@FBGA64 [DX5103]
S29GL128P90DAIS8@FBGA64 [DX5103]
S29GL128P90DFIS7@FBGA64 [DX5103]
S29GL128P90DFIS8@FBGA64 [DX5103]
S29GL128P90FACR1@FBGA64 [DX5074]
S29GL128P90FACR2@FBGA64 [DX5074]
S29GL128P90FAIR1@FBGA64 [DX5074]
S29GL128P90FAIR2@FBGA64 [DX5074]
S29GL128P90FAIS0@FBGA64 [DX5004]
S29GL128P90FAIS7@FBGA64 [DX5074]
S29GL128P90FAIS8@FBGA64 [DX5074]
S29GL128P90FAIS9@FBGA64 [DX5004]
S29GL128P90FASS0@FBGA64 [DX5004]
S29GL128P90FASS7@FBGA64 [DX5074]
S29GL128P90FASS8@FBGA64 [DX5074]
S29GL128P90FASS9@FBGA64 [DX5004]
S29GL128P90FFCR1@FBGA64 [DX5074]
S29GL128P90FFCR2@FBGA64 [DX5074]
S29GL128P90FFIR1@FBGA64 [DX5074]
S29GL128P90FFIR2@FBGA64 [DX5074]
S29GL128P90FFIS0@FBGA64 [DX5004]
S29GL128P90FFIS7@FBGA64 [DX5074]
S29GL128P90FFIS8@FBGA64 [DX5074]
S29GL128P90FFIS9@FBGA64 [DX5004]
S29GL128P90FFSS0@FBGA64 [DX5004]
S29GL128P90FFSS7@FBGA64 [DX5074]
S29GL128P90FFSS8@FBGA64 [DX5074]
S29GL128P90FFSS9@FBGA64 [DX5004]
S29GL128P90TACR1@TSOP56 [DX1011]
S29GL128P90TACR2@TSOP56 [DX1011]
S29GL128P90TAIR1@TSOP56 [DX1011]
S29GL128P90TAIR2@TSOP56 [DX1011]
S29GL128P90TFCR1@TSOP56 [DX1011]
S29GL128P90TFCR2@TSOP56 [DX1011]
S29GL128P90TFIR1@TSOP56 [DX1011]
S29GL128P90TFIR2@TSOP56 [DX1011]
S29GL128S@SSOP56 [DX0051]
S29GL128S10DHI01@FBGA64 [DX5103]
S29GL128S10DHI02@FBGA64 [DX5103]
S29GL128S10DHIV1@FBGA64 [DX5103]
S29GL128S10DHIV2@FBGA64 [DX5103]
S29GL128S10DHSS1@FBGA64 [DX5103]
S29GL128S10DHSS2@FBGA64 [DX5103]
S29GL128S10DHSS3@FBGA64 [DX5103]
S29GL128S10DHSS4@FBGA64 [DX5103]
S29GL128S10DHSS5@FBGA64 [DX5103]
S29GL128S10DHSS6@FBGA64 [DX5103]
S29GL128S10DHSS7@FBGA64 [DX5103]
S29GL128S10DHSS8@FBGA64 [DX5103]
S29GL128S10FHI01@FBGA64 [DX5074]
S29GL128S10FHI02@FBGA64 [DX5074]
S29GL128S10FHIV1@FBGA64 [DX5074]
S29GL128S10FHIV2@FBGA64 [DX5074]
S29GL128S10FHSS1@FBGA64 [DX5074]
S29GL128S10FHSS2@FBGA64 [DX5074]
S29GL128S10FHSS3@FBGA64 [DX5074]
S29GL128S10FHSS4@FBGA64 [DX5074]
S29GL128S10FHSS5@FBGA64 [DX5074]
S29GL128S10FHSS6@FBGA64 [DX5074]
S29GL128S10FHSS7@FBGA64 [DX5074]
S29GL128S10FHSS8@FBGA64 [DX5074]
S29GL128S10TFI01@TSOP56 [DX1011]
S29GL128S10TFI02@TSOP56 [DX1011]
S29GL128S10TFIV1@TSOP56 [DX1011]
S29GL128S10TFIV2@TSOP56 [DX1011]
S29GL128S11DHIV1@FBGA64 [DX5103]
S29GL128S11DHIV2@FBGA64 [DX5103]
S29GL128S11FHIV1@FBGA64 [DX5074]
S29GL128S11FHIV2@FBGA64 [DX5074]
S29GL128S11TFIV1@TSOP56 [DX1011]
S29GL128S11TFIV2@TSOP56 [DX1011]
S29GL128S90DHI01@FBGA64 [DX5103]
S29GL128S90DHI02@FBGA64 [DX5103]
S29GL128S90DHSS1@FBGA64 [DX5103]
S29GL128S90DHSS2@FBGA64 [DX5103]
S29GL128S90DHSS3@FBGA64 [DX5103]
S29GL128S90DHSS4@FBGA64 [DX5103]
S29GL128S90DHSS5@FBGA64 [DX5103]
S29GL128S90DHSS6@FBGA64 [DX5103]
S29GL128S90DHSS7@FBGA64 [DX5103]
S29GL128S90DHSS8@FBGA64 [DX5103]
S29GL128S90FHI01@FBGA64 [DX5074]

S29GL128S90FHI02@FBGA64 [DX5074]
S29GL128S90FHSS1@FBGA64 [DX5074]
S29GL128S90FHSS2@FBGA64 [DX5074]
S29GL128S90FHSS3@FBGA64 [DX5074]
S29GL128S90FHSS4@FBGA64 [DX5074]
S29GL128S90FHSS5@FBGA64 [DX5074]
S29GL128S90FHSS6@FBGA64 [DX5074]
S29GL128S90FHSS7@FBGA64 [DX5074]
S29GL128S90FHSS8@FBGA64 [DX5074]
S29GL128S90GHI01@FBGA56 [DX5045]
S29GL128S90GHI02@FBGA56 [DX5045]
S29GL128S90TFI01@TSOP56 [DX1011]
S29GL128S90TFI02@TSOP56 [DX1011]
S29GL202GP@FBGA54 [DX5004]
S29GL202GS@FBGA54 [DX5004]
S29GL256M10FAIR1@FBGA64 [DX5075]
S29GL256M10FAIR2@FBGA64 [DX5075]
S29GL256M10FFIR1@FBGA64 [DX5075]
S29GL256M10FFIR2@FBGA64 [DX5075]
S29GL256M10TAIR1@TSOP56 [DX1011]
S29GL256M10TAIR2@TSOP56 [DX1011]
S29GL256M10TFIR1@TSOP56 [DX1011]
S29GL256M10TFIR2@TSOP56 [DX1011]
S29GL256M11FAIR1@FBGA64 [DX5075]
S29GL256M11FAIR2@FBGA64 [DX5075]
S29GL256M11FFIR1@FBGA64 [DX5075]
S29GL256M11FFIR2@FBGA64 [DX5075]
S29GL256M11TAIR1@TSOP56 [DX1011]
S29GL256M11TAIR2@TSOP56 [DX1011]
S29GL256M11TFIR1@TSOP56 [DX1011]
S29GL256M11TFIR2@TSOP56 [DX1011]
S29GL256M15TDWN2@TSOP56 [DX1011]
S29GL256N10FAI01@FBGA64 [DX5074]
S29GL256N10FAI02@FBGA64 [DX5074]
S29GL256N10FAIS1@FBGA64 [DX5074]
S29GL256N10FAIS2@FBGA64 [DX5074]
S29GL256N10FAIS3@FBGA64 [DX5004]
S29GL256N10FAIS4@FBGA64 [DX5004]
S29GL256N10FFI01@FBGA64 [DX5074]
S29GL256N10FFI02@FBGA64 [DX5074]
S29GL256N10FFIS1@FBGA64 [DX5074]
S29GL256N10FFIS2@FBGA64 [DX5074]
S29GL256N10FFIS3@FBGA64 [DX5004]
S29GL256N10FFIS4@FBGA64 [DX5004]
S29GL256N10TAI01@TSOP56 [DX1011]
S29GL256N10TAI02@TSOP56 [DX1011]
S29GL256N10TFI01@TSOP56 [DX1011]
S29GL256N10TFI02@TSOP56 [DX1011]
S29GL256N11FAI01@FBGA64 [DX5074]
S29GL256N11FAI02@FBGA64 [DX5074]
S29GL256N11FAIIH@FBGA64 [DX5004]
S29GL256N11FAIS1@FBGA64 [DX5074]
S29GL256N11FAIS2@FBGA64 [DX5074]
S29GL256N11FAIS3@FBGA64 [DX5004]
S29GL256N11FAIS4@FBGA64 [DX5004]
S29GL256N11FAIV1@FBGA64 [DX5074]
S29GL256N11FAIV2@FBGA64 [DX5074]
S29GL256N11FFI01@FBGA64 [DX5074]
S29GL256N11FFI02@FBGA64 [DX5074]
S29GL256N11FFIIH@FBGA64 [DX5004]
S29GL256N11FFIS1@FBGA64 [DX5074]
S29GL256N11FFIS2@FBGA64 [DX5074]
S29GL256N11FFIS3@FBGA64 [DX5004]
S29GL256N11FFIS4@FBGA64 [DX5004]
S29GL256N11FFIV1@FBGA64 [DX5074]
S29GL256N11FFIV2@FBGA64 [DX5074]
S29GL256N11TAI01@TSOP56 [DX1011]
S29GL256N11TAI02@TSOP56 [DX1011]
S29GL256N11TAIV1@TSOP56 [DX1011]
S29GL256N11TAIV2@TSOP56 [DX1011]
S29GL256N11TFI01@TSOP56 [DX1011]
S29GL256N11TFI02@TSOP56 [DX1011]
S29GL256N11TFIV1@TSOP56 [DX1011]
S29GL256N11TFIV2@TSOP56 [DX1011]
S29GL256N90FAIR1@FBGA64 [DX5074]
S29GL256N90FAIR2@FBGA64 [DX5074]
S29GL256N90FFIR1@FBGA64 [DX5074]
S29GL256N90FFIR2@FBGA64 [DX5074]
S29GL256N90TAIR1@TSOP56 [DX1011]
S29GL256N90TAIR2@TSOP56 [DX1011]
S29GL256N90TFIR1@TSOP56 [DX1011]
S29GL256N90TFIR2@TSOP56 [DX1011]
S29GL256NT(low)@TSOP56 [DX1011]
S29GL256P10DAIS1@FBGA64 [DX5103]
S29GL256P10DAIS2@FBGA64 [DX5103]
S29GL256P10DFIS1@FBGA64 [DX5103]
S29GL256P10DFIS2@FBGA64 [DX5103]
S29GL256P10FAI01@FBGA64 [DX5074]
S29GL256P10FAI02@FBGA64 [DX5074]
S29GL256P10FAIS1@FBGA64 [DX5074]
S29GL256P10FAIS2@FBGA64 [DX5074]
S29GL256P10FAIS3@FBGA64 [DX5004]
S29GL256P10FAIS4@FBGA64 [DX5004]
S29GL256P10FFI01@FBGA64 [DX5074]
S29GL256P10FFI02@FBGA64 [DX5074]
S29GL256P10FFIS1@FBGA64 [DX5074]

S29GL256P10FFIS2@FBGA64 [DX5074]
S29GL256P10FFIS3@FBGA64 [DX5004]
S29GL256P10FFIS4@FBGA64 [DX5004]
S29GL256P10TAI01@TSOP56 [DX1011]
S29GL256P10TAI02@TSOP56 [DX1011]
S29GL256P10TFI01@TSOP56 [DX1011]
S29GL256P10TFI02@TSOP56 [DX1011]
S29GL256P11DAIS1@FBGA64 [DX5103]
S29GL256P11DAIS2@FBGA64 [DX5103]
S29GL256P11DAIS5@FBGA64 [DX5103]
S29GL256P11DAIS6@FBGA64 [DX5103]
S29GL256P11DFIS1@FBGA64 [DX5103]
S29GL256P11DFIS2@FBGA64 [DX5103]
S29GL256P11DFIS5@FBGA64 [DX5103]
S29GL256P11DFIS6@FBGA64 [DX5103]
S29GL256P11FAI01@FBGA64 [DX5074]
S29GL256P11FAI02@FBGA64 [DX5074]
S29GL256P11FAIS1@FBGA64 [DX5074]
S29GL256P11FAIS2@FBGA64 [DX5074]
S29GL256P11FAIS3@FBGA64 [DX5004]
S29GL256P11FAIS4@FBGA64 [DX5004]
S29GL256P11FAIS5@FBGA64 [DX5074]
S29GL256P11FAIS6@FBGA64 [DX5074]
S29GL256P11FAIV1@FBGA64 [DX5074]
S29GL256P11FAIV2@FBGA64 [DX5074]
S29GL256P11FFI01@FBGA64 [DX5074]
S29GL256P11FFI02@FBGA64 [DX5074]
S29GL256P11FFIS1@FBGA64 [DX5074]
S29GL256P11FFIS2@FBGA64 [DX5074]
S29GL256P11FFIS3@FBGA64 [DX5004]
S29GL256P11FFIS4@FBGA64 [DX5004]
S29GL256P11FFIS5@FBGA64 [DX5074]
S29GL256P11FFIS6@FBGA64 [DX5074]
S29GL256P11FFIV1@FBGA64 [DX5074]
S29GL256P11FFIV2@FBGA64 [DX5074]
S29GL256P11TAI01@TSOP56 [DX1011]
S29GL256P11TAI02@TSOP56 [DX1011]
S29GL256P11TAIV1@TSOP56 [DX1011]
S29GL256P11TAIV2@TSOP56 [DX1011]
S29GL256P11TFI01@TSOP56 [DX1011]
S29GL256P11TFI02@TSOP56 [DX1011]
S29GL256P11TFIV1@TSOP56 [DX1011]
S29GL256P11TFIV2@TSOP56 [DX1011]
S29GL256P90DAIS7@FBGA64 [DX5103]
S29GL256P90DAIS8@FBGA64 [DX5103]
S29GL256P90DFIS7@FBGA64 [DX5103]
S29GL256P90DFIS8@FBGA64 [DX5103]
S29GL256P90FACR1@FBGA64 [DX5074]
S29GL256P90FACR2@FBGA64 [DX5074]
S29GL256P90FAIR1@FBGA64 [DX5074]
S29GL256P90FAIR2@FBGA64 [DX5074]
S29GL256P90FAIS0@FBGA64 [DX5004]
S29GL256P90FAIS7@FBGA64 [DX5074]
S29GL256P90FAIS8@FBGA64 [DX5074]
S29GL256P90FAIS9@FBGA64 [DX5004]
S29GL256P90FASS0@FBGA64 [DX5004]
S29GL256P90FASS7@FBGA64 [DX5074]
S29GL256P90FASS8@FBGA64 [DX5074]
S29GL256P90FASS9@FBGA64 [DX5004]
S29GL256P90FFCR1@FBGA64 [DX5074]
S29GL256P90FFCR2@FBGA64 [DX5074]
S29GL256P90FFIR1@FBGA64 [DX5074]
S29GL256P90FFIR2@FBGA64 [DX5074]
S29GL256P90FFIS0@FBGA64 [DX5004]
S29GL256P90FFIS7@FBGA64 [DX5074]
S29GL256P90FFIS8@FBGA64 [DX5074]
S29GL256P90FFIS9@FBGA64 [DX5004]
S29GL256P90FFSS0@FBGA64 [DX5004]
S29GL256P90FFSS7@FBGA64 [DX5074]
S29GL256P90FFSS8@FBGA64 [DX5074]
S29GL256P90FFSS9@FBGA64 [DX5004]
S29GL256P90TACR1@TSOP56 [DX1011]
S29GL256P90TACR2@TSOP56 [DX1011]
S29GL256P90TAIR1@TSOP56 [DX1011]
S29GL256P90TAIR2@TSOP56 [DX1011]
S29GL256P90TFCR1@TSOP56 [DX1011]
S29GL256P90TFCR2@TSOP56 [DX1011]
S29GL256P90TFIR1@TSOP56 [DX1011]
S29GL256P90TFIR2@TSOP56 [DX1011]
S29GL256S10DHI01@FBGA64 [DX5103]
S29GL256S10DHI02@FBGA64 [DX5103]
S29GL256S10DHIV1@FBGA64 [DX5103]
S29GL256S10DHIV2@FBGA64 [DX5103]
S29GL256S10DHSS1@FBGA64 [DX5103]
S29GL256S10DHSS2@FBGA64 [DX5103]
S29GL256S10DHSS3@FBGA64 [DX5103]
S29GL256S10DHSS4@FBGA64 [DX5103]
S29GL256S10DHSS5@FBGA64 [DX5103]
S29GL256S10DHSS6@FBGA64 [DX5103]
S29GL256S10DHSS7@FBGA64 [DX5103]
S29GL256S10DHSS8@FBGA64 [DX5103]
S29GL256S10FHI01@FBGA64 [DX5074]
S29GL256S10FHI02@FBGA64 [DX5074]
S29GL256S10FHIV1@FBGA64 [DX5074]
S29GL256S10FHIV2@FBGA64 [DX5074]
S29GL256S10FHSS1@FBGA64 [DX5074]

S29GL256S10FHSS2@FBGA64 [DX5074]
S29GL256S10FHSS3@FBGA64 [DX5074]
S29GL256S10FHSS4@FBGA64 [DX5074]
S29GL256S10FHSS5@FBGA64 [DX5074]
S29GL256S10FHSS6@FBGA64 [DX5074]
S29GL256S10FHSS7@FBGA64 [DX5074]
S29GL256S10FHSS8@FBGA64 [DX5074]
S29GL256S10TFI01@TSOP56 [DX1011]
S29GL256S10TFI02@TSOP56 [DX1011]
S29GL256S10TFIV1@TSOP56 [DX1011]
S29GL256S10TFIV2@TSOP56 [DX1011]
S29GL256S11DHIV1@FBGA64 [DX5103]
S29GL256S11DHIV2@FBGA64 [DX5103]
S29GL256S11FHIV1@FBGA64 [DX5074]
S29GL256S11FHIV2@FBGA64 [DX5074]
S29GL256S11TFIV1@TSOP56 [DX1011]
S29GL256S11TFIV2@TSOP56 [DX1011]
S29GL256S90DHI01@FBGA64 [DX5103]
S29GL256S90DHI02@FBGA64 [DX5103]
S29GL256S90DHSS1@FBGA64 [DX5103]
S29GL256S90DHSS2@FBGA64 [DX5103]
S29GL256S90DHSS3@FBGA64 [DX5103]
S29GL256S90DHSS4@FBGA64 [DX5103]
S29GL256S90DHSS5@FBGA64 [DX5103]
S29GL256S90DHSS6@FBGA64 [DX5103]
S29GL256S90DHSS7@FBGA64 [DX5103]
S29GL256S90DHSS8@FBGA64 [DX5103]
S29GL256S90FHI01@FBGA64 [DX5074]
S29GL256S90FHI02@FBGA64 [DX5074]
S29GL256S90FHSS1@FBGA64 [DX5074]
S29GL256S90FHSS2@FBGA64 [DX5074]
S29GL256S90FHSS3@FBGA64 [DX5074]
S29GL256S90FHSS4@FBGA64 [DX5074]
S29GL256S90FHSS5@FBGA64 [DX5074]
S29GL256S90FHSS6@FBGA64 [DX5074]
S29GL256S90FHSS7@FBGA64 [DX5074]
S29GL256S90FHSS8@FBGA64 [DX5074]
S29GL256S90GHI01@FBGA56 [DX5045]
S29GL256S90GHI02@FBGA56 [DX5045]
S29GL256S90TFI01@TSOP56 [DX1011]
S29GL256S90TFI02@TSOP56 [DX1011]
S29GL512N10FAI01@FBGA64 [DX5074]
S29GL512N10FAI02@FBGA64 [DX5074]
S29GL512N10FAIS1@FBGA64 [DX5074]
S29GL512N10FAIS2@FBGA64 [DX5074]
S29GL512N10FFI01@FBGA64 [DX5074]
S29GL512N10FFI02@FBGA64 [DX5074]
S29GL512N10FFIS1@FBGA64 [DX5074]
S29GL512N10FFIS2@FBGA64 [DX5074]
S29GL512N10TAI01@TSOP56 [DX1011]
S29GL512N10TAI02@TSOP56 [DX1011]
S29GL512N10TFI01@TSOP56 [DX1011]
S29GL512N10TFI02@TSOP56 [DX1011]
S29GL512N11FAI01@FBGA64 [DX5074]
S29GL512N11FAI02@FBGA64 [DX5074]
S29GL512N11FAIS1@FBGA64 [DX5074]
S29GL512N11FAIS2@FBGA64 [DX5074]
S29GL512N11FAIV1@FBGA64 [DX5074]
S29GL512N11FAIV2@FBGA64 [DX5074]
S29GL512N11FFI01@FBGA64 [DX5074]
S29GL512N11FFI02@FBGA64 [DX5074]
S29GL512N11FFIS1@FBGA64 [DX5074]
S29GL512N11FFIS2@FBGA64 [DX5074]
S29GL512N11FFIV1@FBGA64 [DX5074]
S29GL512N11FFIV2@FBGA64 [DX5074]
S29GL512N11TAI01@TSOP56 [DX1011]
S29GL512N11TAI02@TSOP56 [DX1011]
S29GL512N11TAIV1@TSOP56 [DX1011]
S29GL512N11TAIV2@TSOP56 [DX1011]
S29GL512N11TFI01@TSOP56 [DX1011]
S29GL512N11TFI02@TSOP56 [DX1011]
S29GL512N11TFIV1@TSOP56 [DX1011]
S29GL512N11TFIV2@TSOP56 [DX1011]
S29GL512P10DAIS1@FBGA64 [DX5103]
S29GL512P10DAIS2@FBGA64 [DX5103]
S29GL512P10DAIS7@FBGA64 [DX5103]
S29GL512P10DAIS8@FBGA64 [DX5103]
S29GL512P10DFIS1@FBGA64 [DX5103]
S29GL512P10DFIS2@FBGA64 [DX5103]
S29GL512P10DFIS7@FBGA64 [DX5103]
S29GL512P10DFIS8@FBGA64 [DX5103]
S29GL512P10FACR1@FBGA64 [DX5074]
S29GL512P10FACR2@FBGA64 [DX5074]
S29GL512P10FAI01@FBGA64 [DX5074]
S29GL512P10FAI02@FBGA64 [DX5074]
S29GL512P10FAIR1@FBGA64 [DX5074]
S29GL512P10FAIR2@FBGA64 [DX5074]
S29GL512P10FAIS1@FBGA64 [DX5074]
S29GL512P10FAIS2@FBGA64 [DX5074]
S29GL512P10FAIS7@FBGA64 [DX5074]
S29GL512P10FAIS8@FBGA64 [DX5074]
S29GL512P10FASS7@FBGA64 [DX5074]
S29GL512P10FASS8@FBGA64 [DX5074]
S29GL512P10FFCR1@FBGA64 [DX5074]
S29GL512P10FFCR2@FBGA64 [DX5074]
S29GL512P10FFI01@FBGA64 [DX5074]

S29GL512P10FFI02@FBGA64 [DX5074]
S29GL512P10FFIR1@FBGA64 [DX5074]
S29GL512P10FFIR2@FBGA64 [DX5074]
S29GL512P10FFIS1@FBGA64 [DX5074]
S29GL512P10FFIS2@FBGA64 [DX5074]
S29GL512P10FFIS7@FBGA64 [DX5074]
S29GL512P10FFIS8@FBGA64 [DX5074]
S29GL512P10FFSS7@FBGA64 [DX5074]
S29GL512P10FFSS8@FBGA64 [DX5074]
S29GL512P10TACR1@TSOP56 [DX1011]
S29GL512P10TACR2@TSOP56 [DX1011]
S29GL512P10TAI01@TSOP56 [DX1011]
S29GL512P10TAI02@TSOP56 [DX1011]
S29GL512P10TAIR1@TSOP56 [DX1011]
S29GL512P10TAIR2@TSOP56 [DX1011]
S29GL512P10TFCR1@TSOP56 [DX1011]
S29GL512P10TFCR2@TSOP56 [DX1011]
S29GL512P10TFI01@TSOP56 [DX1011]
S29GL512P10TFI02@TSOP56 [DX1011]
S29GL512P10TFIR1@TSOP56 [DX1011]
S29GL512P10TFIR2@TSOP56 [DX1011]
S29GL512P11DAIS1@FBGA64 [DX5103]
S29GL512P11DAIS2@FBGA64 [DX5103]
S29GL512P11DAIS5@FBGA64 [DX5103]
S29GL512P11DAIS6@FBGA64 [DX5103]
S29GL512P11DFIS1@FBGA64 [DX5103]
S29GL512P11DFIS2@FBGA64 [DX5103]
S29GL512P11DFIS5@FBGA64 [DX5103]
S29GL512P11DFIS6@FBGA64 [DX5103]
S29GL512P11FAI01@FBGA64 [DX5074]
S29GL512P11FAI02@FBGA64 [DX5074]
S29GL512P11FAIS1@FBGA64 [DX5074]
S29GL512P11FAIS2@FBGA64 [DX5074]
S29GL512P11FAIS5@FBGA64 [DX5074]
S29GL512P11FAIS6@FBGA64 [DX5074]
S29GL512P11FAIV1@FBGA64 [DX5074]
S29GL512P11FAIV2@FBGA64 [DX5074]
S29GL512P11FFI01@FBGA64 [DX5074]
S29GL512P11FFI02@FBGA64 [DX5074]
S29GL512P11FFIS1@FBGA64 [DX5074]
S29GL512P11FFIS2@FBGA64 [DX5074]
S29GL512P11FFIS5@FBGA64 [DX5074]
S29GL512P11FFIS6@FBGA64 [DX5074]
S29GL512P11FFIV1@FBGA64 [DX5074]
S29GL512P11FFIV2@FBGA64 [DX5074]
S29GL512P11TAI01@TSOP56 [DX1011]
S29GL512P11TAI02@TSOP56 [DX1011]
S29GL512P11TAIV1@TSOP56 [DX1011]
S29GL512P11TAIV2@TSOP56 [DX1011]
S29GL512P11TFI01@TSOP56 [DX1011]
S29GL512P11TFI02@TSOP56 [DX1011]
S29GL512P11TFIV1@TSOP56 [DX1011]
S29GL512P11TFIV2@TSOP56 [DX1011]
S29GL512P12DAIS5@FBGA64 [DX5103]
S29GL512P12DAIS6@FBGA64 [DX5103]
S29GL512P12DFIS5@FBGA64 [DX5103]
S29GL512P12DFIS6@FBGA64 [DX5103]
S29GL512P12FAIS5@FBGA64 [DX5074]
S29GL512P12FAIS6@FBGA64 [DX5074]
S29GL512P12FAIV1@FBGA64 [DX5074]
S29GL512P12FAIV2@FBGA64 [DX5074]
S29GL512P12FFIS5@FBGA64 [DX5074]
S29GL512P12FFIS6@FBGA64 [DX5074]
S29GL512P12FFIV1@FBGA64 [DX5074]
S29GL512P12FFIV2@FBGA64 [DX5074]
S29GL512P12TAIV1@TSOP56 [DX1011]
S29GL512P12TAIV2@TSOP56 [DX1011]
S29GL512P12TFIV1@TSOP56 [DX1011]
S29GL512P12TFIV2@TSOP56 [DX1011]
S29GL512R10FFCR1@FBGA64 [DX5103]
S29GL512R10FFCR2@FBGA64 [DX5103]
S29GL512R10FFCS7@FBGA64 [DX5103]
S29GL512R10FFCS8@FBGA64 [DX5103]
S29GL512R10FFIR1@FBGA64 [DX5103]
S29GL512R10FFIR2@FBGA64 [DX5103]
S29GL512R10TFCR1@TSOP56 [DX1011]
S29GL512R10TFCR2@TSOP56 [DX1011]
S29GL512R10TFIR1@TSOP56 [DX1011]
S29GL512R10TFIR2@TSOP56 [DX1011]
S29GL512R11DFI01@FBGA64 [DX5074]
S29GL512R11DFI02@FBGA64 [DX5074]
S29GL512R11TFI01@TSOP56 [DX1011]
S29GL512R11TFI02@TSOP56 [DX1011]
S29GL512R12DFIV1@FBGA64 [DX5074]
S29GL512R12DFIV2@FBGA64 [DX5074]
S29GL512R12TFIV1@TSOP56 [DX1011]
S29GL512R12TFIV2@TSOP56 [DX1011]
S29GL512S10DHI01@FBGA64 [DX5103]
S29GL512S10DHI02@FBGA64 [DX5103]
S29GL512S10DHIV1@FBGA64 [DX5103]
S29GL512S10DHIV2@FBGA64 [DX5103]
S29GL512S10DHSS1@FBGA64 [DX5103]
S29GL512S10DHSS2@FBGA64 [DX5103]
S29GL512S10DHSS3@FBGA64 [DX5103]
S29GL512S10DHSS4@FBGA64 [DX5103]
S29GL512S10DHSS5@FBGA64 [DX5103]

S29GL512S10DHSS6@FBGA64 [DX5103]
S29GL512S10DHSS7@FBGA64 [DX5103]
S29GL512S10DHSS8@FBGA64 [DX5103]
S29GL512S10FHI01@FBGA64 [DX5074]
S29GL512S10FHI02@FBGA64 [DX5074]
S29GL512S10FHSS1@FBGA64 [DX5074]
S29GL512S10FHSS2@FBGA64 [DX5074]
S29GL512S10FHSS3@FBGA64 [DX5074]
S29GL512S10FHSS4@FBGA64 [DX5074]
S29GL512S10FHSS5@FBGA64 [DX5074]
S29GL512S10FHSS6@FBGA64 [DX5074]
S29GL512S10FHSS7@FBGA64 [DX5074]
S29GL512S10FHSS8@FBGA64 [DX5074]
S29GL512S10GHI01@FBGA56 [DX5045]
S29GL512S10GHI02@FBGA56 [DX5045]
S29GL512S10TFI01@TSOP56 [DX1011]
S29GL512S10TFI02@TSOP56 [DX1011]
S29GL512S11DHI01@FBGA64 [DX5103]
S29GL512S11DHI02@FBGA64 [DX5103]
S29GL512S11DHIV1@FBGA64 [DX5103]
S29GL512S11DHIV2@FBGA64 [DX5103]
S29GL512S11DHSS1@FBGA64 [DX5103]
S29GL512S11DHSS2@FBGA64 [DX5103]
S29GL512S11DHSS3@FBGA64 [DX5103]
S29GL512S11DHSS4@FBGA64 [DX5103]
S29GL512S11DHSS5@FBGA64 [DX5103]
S29GL512S11DHSS6@FBGA64 [DX5103]
S29GL512S11DHSS7@FBGA64 [DX5103]
S29GL512S11DHSS8@FBGA64 [DX5103]
S29GL512S11FHI01@FBGA64 [DX5074]
S29GL512S11FHI02@FBGA64 [DX5074]
S29GL512S11FHIV1@FBGA64 [DX5074]
S29GL512S11FHIV2@FBGA64 [DX5074]
S29GL512S11FHSS1@FBGA64 [DX5074]
S29GL512S11FHSS2@FBGA64 [DX5074]
S29GL512S11FHSS3@FBGA64 [DX5074]
S29GL512S11FHSS4@FBGA64 [DX5074]
S29GL512S11FHSS5@FBGA64 [DX5074]
S29GL512S11FHSS6@FBGA64 [DX5074]
S29GL512S11FHSS7@FBGA64 [DX5074]
S29GL512S11FHSS8@FBGA64 [DX5074]
S29GL512S11TFI01@TSOP56 [DX1011]
S29GL512S11TFI02@TSOP56 [DX1011]
S29GL512S11TFIV1@TSOP56 [DX1011]
S29GL512S11TFIV2@TSOP56 [DX1011]
S29GL512S12DHIV1@FBGA64 [DX5103]
S29GL512S12DHIV2@FBGA64 [DX5103]
S29GL512S12FHIV1@FBGA64 [DX5074]
S29GL512S12FHIV2@FBGA64 [DX5074]
S29GL512S12TFIV1@TSOP56 [DX1011]
S29GL512S12TFIV2@TSOP56 [DX1011]
S29GL512T10DHI01@FBGA64 [DX5103]
S29GL512T10DHI02@FBGA64 [DX5103]
S29GL512T10FHI01@FBGA64 [DX5074]
S29GL512T10FHI02@FBGA64 [DX5074]
S29GL512T10GHI01@FBGA56 [DX5045]
S29GL512T10GHI02@FBGA56 [DX5045]
S29GL512T10TFI01@TSOP56 [DX1011]
S29GL512T10TFI02@TSOP56 [DX1011]
S29GL512T11DHIV1@FBGA64 [DX5103]
S29GL512T11DHIV2@FBGA64 [DX5103]
S29GL512T11DHV01@FBGA64 [DX5103]
S29GL512T11DHV02@FBGA64 [DX5103]
S29GL512T11FHI01@FBGA64 [DX5074]
S29GL512T11FHI02@FBGA64 [DX5074]
S29GL512T11TFIV1@TSOP56 [DX1011]
S29GL512T11TFIV2@TSOP56 [DX1011]
S29GL512T11TFV01@TSOP56 [DX1011]
S29GL512T11TFV02@TSOP56 [DX1011]
S29GL512T12DHVV1@FBGA64 [DX5103]
S29GL512T12DHVV2@FBGA64 [DX5103]
S29GL512T12TFVV1@TSOP56 [DX1011]
S29GL512T12TFVV2@TSOP56 [DX1011]
S29JL032H55BAI01@FBGA48 [DX5043]
S29JL032H55BAI02@FBGA48 [DX5043]
S29JL032H55BAI21@FBGA48 [DX5043]
S29JL032H55BAI22@FBGA48 [DX5043]
S29JL032H55BAI31@FBGA48 [DX5043]
S29JL032H55BAI32@FBGA48 [DX5043]
S29JL032H55BAI41@FBGA48 [DX5043]
S29JL032H55BAI42@FBGA48 [DX5043]
S29JL032H55BFI01@FBGA48 [DX5043]
S29JL032H55BFI02@FBGA48 [DX5043]
S29JL032H55BFI21@FBGA48 [DX5043]
S29JL032H55BFI22@FBGA48 [DX5043]
S29JL032H55BFI31@FBGA48 [DX5043]
S29JL032H55BFI32@FBGA48 [DX5043]
S29JL032H55BFI41@FBGA48 [DX5043]
S29JL032H55BFI42@FBGA48 [DX5043]
S29JL032H55TAI01@TSOP48 [DX1004]
S29JL032H55TAI02@TSOP48 [DX1004]
S29JL032H55TAI21@TSOP48 [DX1004]
S29JL032H55TAI22@TSOP48 [DX1004]
S29JL032H55TAI31@TSOP48 [DX1004]
S29JL032H55TAI32@TSOP48 [DX1004]
S29JL032H55TAI41@TSOP48 [DX1004]

S29JL032H55TAI42@TSOP48 [DX1004]
S29JL032H55TFI01@TSOP48 [DX1004]
S29JL032H55TFI02@TSOP48 [DX1004]
S29JL032H55TFI21@TSOP48 [DX1004]
S29JL032H55TFI22@TSOP48 [DX1004]
S29JL032H55TFI31@TSOP48 [DX1004]
S29JL032H55TFI32@TSOP48 [DX1004]
S29JL032H55TFI41@TSOP48 [DX1004]
S29JL032H55TFI42@TSOP48 [DX1004]
S29JL032H60BAI01@FBGA48 [DX5043]
S29JL032H60BAI02@FBGA48 [DX5043]
S29JL032H60BAI21@FBGA48 [DX5043]
S29JL032H60BAI22@FBGA48 [DX5043]
S29JL032H60BAI31@FBGA48 [DX5043]
S29JL032H60BAI32@FBGA48 [DX5043]
S29JL032H60BAI41@FBGA48 [DX5043]
S29JL032H60BAI42@FBGA48 [DX5043]
S29JL032H60BFI01@FBGA48 [DX5043]
S29JL032H60BFI02@FBGA48 [DX5043]
S29JL032H60BFI21@FBGA48 [DX5043]
S29JL032H60BFI22@FBGA48 [DX5043]
S29JL032H60BFI31@FBGA48 [DX5043]
S29JL032H60BFI32@FBGA48 [DX5043]
S29JL032H60BFI41@FBGA48 [DX5043]
S29JL032H60BFI42@FBGA48 [DX5043]
S29JL032H60TAI01@TSOP48 [DX1004]
S29JL032H60TAI02@TSOP48 [DX1004]
S29JL032H60TAI21@TSOP48 [DX1004]
S29JL032H60TAI22@TSOP48 [DX1004]
S29JL032H60TAI31@TSOP48 [DX1004]
S29JL032H60TAI32@TSOP48 [DX1004]
S29JL032H60TAI41@TSOP48 [DX1004]
S29JL032H60TAI42@TSOP48 [DX1004]
S29JL032H60TFI01@TSOP48 [DX1004]
S29JL032H60TFI02@TSOP48 [DX1004]
S29JL032H60TFI21@TSOP48 [DX1004]
S29JL032H60TFI22@TSOP48 [DX1004]
S29JL032H60TFI31@TSOP48 [DX1004]
S29JL032H60TFI32@TSOP48 [DX1004]
S29JL032H60TFI41@TSOP48 [DX1004]
S29JL032H60TFI42@TSOP48 [DX1004]
S29JL032H70BAI01@FBGA48 [DX5043]
S29JL032H70BAI02@FBGA48 [DX5043]
S29JL032H70BAI21@FBGA48 [DX5043]
S29JL032H70BAI22@FBGA48 [DX5043]
S29JL032H70BAI31@FBGA48 [DX5043]
S29JL032H70BAI32@FBGA48 [DX5043]
S29JL032H70BAI41@FBGA48 [DX5043]
S29JL032H70BAI42@FBGA48 [DX5043]
S29JL032H70BFI01@FBGA48 [DX5043]
S29JL032H70BFI02@FBGA48 [DX5043]
S29JL032H70BFI21@FBGA48 [DX5043]
S29JL032H70BFI22@FBGA48 [DX5043]
S29JL032H70BFI31@FBGA48 [DX5043]
S29JL032H70BFI32@FBGA48 [DX5043]
S29JL032H70BFI41@FBGA48 [DX5043]
S29JL032H70BFI42@FBGA48 [DX5043]
S29JL032H70TAI01@TSOP48 [DX1004]
S29JL032H70TAI02@TSOP48 [DX1004]
S29JL032H70TAI21@TSOP48 [DX1004]
S29JL032H70TAI22@TSOP48 [DX1004]
S29JL032H70TAI31@TSOP48 [DX1004]
S29JL032H70TAI32@TSOP48 [DX1004]
S29JL032H70TAI41@TSOP48 [DX1004]
S29JL032H70TAI42@TSOP48 [DX1004]
S29JL032H70TFI01@TSOP48 [DX1004]
S29JL032H70TFI02@TSOP48 [DX1004]
S29JL032H70TFI21@TSOP48 [DX1004]
S29JL032H70TFI22@TSOP48 [DX1004]
S29JL032H70TFI31@TSOP48 [DX1004]
S29JL032H70TFI32@TSOP48 [DX1004]
S29JL032H70TFI41@TSOP48 [DX1004]
S29JL032H70TFI42@TSOP48 [DX1004]
S29JL032H70TFIG1@TSOP48 [DX1043]
S29JL032H90BAI01@FBGA48 [DX5043]
S29JL032H90BAI02@FBGA48 [DX5043]
S29JL032H90BAI21@FBGA48 [DX5043]
S29JL032H90BAI22@FBGA48 [DX5043]
S29JL032H90BAI31@FBGA48 [DX5043]
S29JL032H90BAI32@FBGA48 [DX5043]
S29JL032H90BAI41@FBGA48 [DX5043]
S29JL032H90BAI42@FBGA48 [DX5043]
S29JL032H90BFI01@FBGA48 [DX5043]
S29JL032H90BFI02@FBGA48 [DX5043]
S29JL032H90BFI21@FBGA48 [DX5043]
S29JL032H90BFI22@FBGA48 [DX5043]
S29JL032H90BFI31@FBGA48 [DX5043]
S29JL032H90BFI32@FBGA48 [DX5043]
S29JL032H90BFI41@FBGA48 [DX5043]
S29JL032H90BFI42@FBGA48 [DX5043]
S29JL032H90TAI01@TSOP48 [DX1004]
S29JL032H90TAI02@TSOP48 [DX1004]
S29JL032H90TAI21@TSOP48 [DX1004]
S29JL032H90TAI22@TSOP48 [DX1004]
S29JL032H90TAI31@TSOP48 [DX1004]
S29JL032H90TAI32@TSOP48 [DX1004]

S29JL032H90TAI41@TSOP48 [DX1004]
S29JL032H90TAI42@TSOP48 [DX1004]
S29JL032H90TFI01@TSOP48 [DX1004]
S29JL032H90TFI02@TSOP48 [DX1004]
S29JL032H90TFI21@TSOP48 [DX1004]
S29JL032H90TFI22@TSOP48 [DX1004]
S29JL032H90TFI31@TSOP48 [DX1004]
S29JL032H90TFI32@TSOP48 [DX1004]
S29JL032H90TFI41@TSOP48 [DX1004]
S29JL032H90TFI42@TSOP48 [DX1004]
S29JL032J60BHI31@FBGA48 [DX5043]
S29JL032J60BHI32@FBGA48 [DX5043]
S29JL032J60TFI01@TSOP48 [DX1004]
S29JL032J60TFI02@TSOP48 [DX1004]
S29JL032J60TFI21@TSOP48 [DX1004]
S29JL032J60TFI22@TSOP48 [DX1004]
S29JL032J60TFI31@TSOP48 [DX1004]
S29JL032J60TFI32@TSOP48 [DX1004]
S29JL032J60TFI41@TSOP48 [DX1004]
S29JL032J60TFI42@TSOP48 [DX1004]
S29JL032J70BHI31@FBGA48 [DX5043]
S29JL032J70BHI32@FBGA48 [DX5043]
S29JL032J70TFI01@TSOP48 [DX1004]
S29JL032J70TFI02@TSOP48 [DX1004]
S29JL032J70TFI21@TSOP48 [DX1004]
S29JL032J70TFI22@TSOP48 [DX1004]
S29JL032J70TFI31@TSOP48 [DX1004]
S29JL032J70TFI32@TSOP48 [DX1004]
S29JL032J70TFI41@TSOP48 [DX1004]
S29JL032J70TFI42@TSOP48 [DX1004]
S29JL064H55BAI00@FBGA63 [DX5041]
S29JL064H55BFI00@FBGA63 [DX5041]
S29JL064H55TAI00@TSOP48 [DX1004]
S29JL064H55TFI00@TSOP48 [DX1004]
S29JL064H60BAI00@FBGA63 [DX5041]
S29JL064H60BFI00@FBGA63 [DX5041]
S29JL064H60TAI00@TSOP48 [DX1004]
S29JL064H60TFI00@TSOP48 [DX1004]
S29JL064H70BAI00@FBGA63 [DX5041]
S29JL064H70BFI00@FBGA63 [DX5041]
S29JL064H70TAI00@TSOP48 [DX1004]
S29JL064H70TAN00@TSOP48 [DX1004]
S29JL064H70TFI00@TSOP48 [DX1004]
S29JL064H70TFN00@TSOP48 [DX1004]
S29JL064H90BAI00@FBGA63 [DX5041]
S29JL064H90BFI00@FBGA63 [DX5041]
S29JL064H90TAI00@TSOP48 [DX1004]
S29JL064H90TAN00@TSOP48 [DX1004]
S29JL064H90TFI00@TSOP48 [DX1004]
S29JL064H90TFN00@TSOP48 [DX1004]
S29JL064J55BHI00@FBGA48 [DX5043]
S29JL064J55TFI00@TSOP48 [DX1004]
S29JL064J60BHI00@FBGA48 [DX5043]
S29JL064J60TFI00@TSOP48 [DX1004]
S29JL064J70BHI00@FBGA48 [DX5043]
S29JL064J70TFI00@TSOP48 [DX1004]
S29NS016J0LBFW00@FBGA44 [DX5094]
S29NS016J0LBJW00@FBGA44 [DX5094]
S29NS016J0PBFW00@FBGA44 [DX5094]
S29NS016J0PBJW00@FBGA44 [DX5094]
S29NS032J0LBFW00@FBGA44 [DX5094]
S29NS032J0LBJW00@FBGA44 [DX5094]
S29NS032J0PBFW00@FBGA44 [DX5094]
S29NS032J0PBJW00@FBGA44 [DX5094]
S29NS064J0LBAW00@FBGA44 [DX5066]
S29NS064J0LBFW00@FBGA44 [DX5066]
S29NS064J0LBJW00@FBGA44 [DX5066]
S29NS064J0PBAW00@FBGA44 [DX5066]
S29NS064J0PBFW00@FBGA44 [DX5066]
S29NS064J0PBJW00@FBGA44 [DX5066]
S29NS064N0PBJW00@FBGA44 [DX5067]
S29NS128J0LBAW00@FBGA48 [DX50UN]
S29NS128J0LBFW00@FBGA48 [DX50UN]
S29NS128J0LBJW00@FBGA48 [DX50UN]
S29NS128J0PBAW00@FBGA48 [DX50UN]
S29NS128J0PBFW00@FBGA48 [DX50UN]
S29NS128J0PBJW00@FBGA48 [DX50UN]
S29NS128N0PBJW00@FBGA44 [DX5066]
S29NS128P0PBJW00@FBGA44 [DX5067]
S29NS128P0SBJW00@FBGA44 [DX5067]
S29NS128PABBJW00@FBGA44 [DX5067]
S29NS128R0PBHW00@FBGA44 [DX5067]
S29NS128R0SBHW00@FBGA44 [DX5067]
S29NS128RAABHW00@FBGA44 [DX5067]
S29NS256N0PBJW00@FBGA48 [DX50UN]
S29NS256P0PBJW00@FBGA44 [DX5067]
S29NS256P0SBJW00@FBGA44 [DX5067]
S29NS256PABBJW00@FBGA44 [DX5067]
S29NS256R0PBHW00@FBGA44 [DX5067]
S29NS256R0SBHW00@FBGA44 [DX5067]
S29NS256RAABHW00@FBGA44 [DX5067]
S29NS512P0PBJW00@FBGA64 [DX5066]
S29NS512P0SBJW00@FBGA64 [DX5066]
S29NS512PABBJW00@FBGA64 [DX5066]
S29PL032J55BAI12@FBGA48 [DX5043]
S29PL032J55BAI15@FBGA56 [DX5045]

S29PL032J55BAW12@FBGA48 [DX5043]	S29PL032J55BAW15@FBGA56 [DX5045]
S29PL032J55BFI12@FBGA48 [DX5043]	S29PL032J55BFI15@FBGA56 [DX5045]
S29PL032J55BFW12@FBGA48 [DX5043]	S29PL032J55BFW15@FBGA56 [DX5045]
S29PL032J60BAI12@FBGA48 [DX5043]	S29PL032J60BAI15@FBGA56 [DX5045]
S29PL032J60BAW12@FBGA48 [DX5043]	S29PL032J60BAW15@FBGA56 [DX5045]
S29PL032J60BFI12@FBGA48 [DX5043]	S29PL032J60BFI15@FBGA56 [DX5045]
S29PL032J60BFW12@FBGA48 [DX5043]	S29PL032J60BFW15@FBGA56 [DX5045]
S29PL032J70BAI12@FBGA48 [DX5043]	S29PL032J70BAI15@FBGA56 [DX5045]
S29PL032J70BAW12@FBGA48 [DX5043]	S29PL032J70BAW15@FBGA56 [DX5045]
S29PL032J70BFI12@FBGA48 [DX5043]	S29PL032J70BFI15@FBGA56 [DX5045]
S29PL032J70BFW12@FBGA48 [DX5043]	S29PL032J70BFW15@FBGA56 [DX5045]
S29PL064J55BAI12@FBGA48 [DX5043]	S29PL064J55BAI15@FBGA56 [DX5045]
S29PL064J55BAW12@FBGA48 [DX5043]	S29PL064J55BAW15@FBGA56 [DX5045]
S29PL064J55BFI12@FBGA48 [DX5043]	S29PL064J55BFI15@FBGA56 [DX5045]
S29PL064J55BFW12@FBGA48 [DX5043]	S29PL064J55BFW15@FBGA56 [DX5045]
S29PL064J60BAI12@FBGA48 [DX5043]	S29PL064J60BAI15@FBGA56 [DX5045]
S29PL064J60BAW12@FBGA48 [DX5043]	S29PL064J60BAW15@FBGA56 [DX5045]
S29PL064J60BFI12@FBGA48 [DX5043]	S29PL064J60BFI15@FBGA56 [DX5045]
S29PL064J60BFW12@FBGA48 [DX5043]	S29PL064J60BFW15@FBGA56 [DX5045]
S29PL064J70BAI12@FBGA48 [DX5043]	S29PL064J70BAI15@FBGA56 [DX5045]
S29PL064J70BAW12@FBGA48 [DX5043]	S29PL064J70BAW15@FBGA56 [DX5045]
S29PL064J70BFI12@FBGA48 [DX5043]	S29PL064J70BFI15@FBGA56 [DX5045]
S29PL064J70BFW12@FBGA48 [DX5043]	S29PL064J70BFW15@FBGA56 [DX5045]
S29PL127J55BAI00@FBGA80 [DX5001]	S29PL127J55BAI02@FBGA64 [DX5001]
S29PL127J55BAW00@FBGA80 [DX5001]	S29PL127J55BAW02@FBGA64 [DX5001]
S29PL127J55BFI00@FBGA80 [DX5001]	S29PL127J55BFI02@FBGA64 [DX5001]
S29PL127J55BFW00@FBGA80 [DX5001]	S29PL127J55BFW02@FBGA64 [DX5001]
S29PL127J55TAI13@TSOP56 [DX1011]	S29PL127J55TAW13@TSOP56 [DX1011]
S29PL127J55TFI13@TSOP56 [DX1011]	S29PL127J55TFW13@TSOP56 [DX1011]
S29PL127J60BAI00@FBGA80 [DX5001]	S29PL127J60BAI02@FBGA64 [DX5001]
S29PL127J60BAW00@FBGA80 [DX5001]	S29PL127J60BAW02@FBGA64 [DX5001]
S29PL127J60BFI00@FBGA80 [DX5001]	S29PL127J60BFI02@FBGA64 [DX5001]
S29PL127J60BFW00@FBGA80 [DX5001]	S29PL127J60BFW02@FBGA64 [DX5001]
S29PL127J60TAI13@TSOP56 [DX1011]	S29PL127J60TAW13@TSOP56 [DX1011]
S29PL127J60TFI13@TSOP56 [DX1011]	S29PL127J60TFW13@TSOP56 [DX1011]
S29PL127J65BAI00@FBGA80 [DX5001]	S29PL127J65BAI01@FBGA80 [DX5001]
S29PL127J65BAI02@FBGA64 [DX5001]	S29PL127J65BAW00@FBGA80 [DX5001]
S29PL127J65BAW01@FBGA80 [DX5001]	S29PL127J65BAW02@FBGA64 [DX5001]
S29PL127J65BFI00@FBGA80 [DX5001]	S29PL127J65BFI01@FBGA80 [DX5001]
S29PL127J65BFI02@FBGA64 [DX5001]	S29PL127J65BFW00@FBGA80 [DX5001]
S29PL127J65BFW01@FBGA80 [DX5001]	S29PL127J65BFW02@FBGA64 [DX5001]
S29PL127J70BAI00@FBGA80 [DX5001]	S29PL127J70BAI01@FBGA80 [DX5001]
S29PL127J70BAI02@FBGA64 [DX5001]	S29PL127J70BAW00@FBGA80 [DX5001]
S29PL127J70BAW01@FBGA80 [DX5001]	S29PL127J70BAW02@FBGA64 [DX5001]
S29PL127J70BFI00@FBGA80 [DX5001]	S29PL127J70BFI01@FBGA80 [DX5001]
S29PL127J70BFI02@FBGA64 [DX5001]	S29PL127J70BFW00@FBGA80 [DX5001]
S29PL127J70BFW01@FBGA80 [DX5001]	S29PL127J70BFW02@FBGA64 [DX5001]
S29PL127J70TAI13@TSOP56 [DX1011]	S29PL127J70TAW13@TSOP56 [DX1011]

S29PL127J70TFI13@TSOP56 [DX1011]
S29PL127J70TFW13@TSOP56 [DX1011]
S29PL127N60GAI00@FBGA64 [DX5001]
S29PL127N60GAW00@FBGA64 [DX5001]
S29PL127N60GFI00@FBGA64 [DX5001]
S29PL127N60GFW00@FBGA64 [DX5001]
S29PL127N65GAI00@FBGA64 [DX5001]
S29PL127N65GAW00@FBGA64 [DX5001]
S29PL127N65GAWW0@FBGA64 [DX5001]
S29PL127N65GFI00@FBGA64 [DX5001]
S29PL127N65GFW00@FBGA64 [DX5001]
S29PL127N65GFWW0@FBGA64 [DX5001]
S29PL127N70GAI00@FBGA64 [DX5001]
S29PL127N70GAW00@FBGA64 [DX5001]
S29PL127N70GAWW0@FBGA64 [DX5001]
S29PL127N70GFI00@FBGA64 [DX5001]
S29PL127N70GFW00@FBGA64 [DX5001]
S29PL127N70GFWW0@FBGA64 [DX5001]
S29PL129N60GAI00@FBGA64 [DX5001]
S29PL129N60GAW00@FBGA64 [DX5001]
S29PL129N60GFI00@FBGA64 [DX5001]
S29PL129N60GFW00@FBGA64 [DX5001]
S29PL129N65GAI00@FBGA64 [DX5001]
S29PL129N65GAW00@FBGA64 [DX5001]
S29PL129N65GAWW0@FBGA64 [DX5001]
S29PL129N65GFI00@FBGA64 [DX5001]
S29PL129N65GFW00@FBGA64 [DX5001]
S29PL129N65GFWW0@FBGA64 [DX5001]
S29PL129N70GAI00@FBGA64 [DX5001]
S29PL129N70GAW00@FBGA64 [DX5001]
S29PL129N70GAWW0@FBGA64 [DX5001]
S29PL129N70GFI00@FBGA64 [DX5001]
S29PL129N70GFW00@FBGA64 [DX5001]
S29PL129N70GFWW0@FBGA64 [DX5001]
S29PL256N60GAI00@FBGA84 [DX5001]
S29PL256N60GAW00@FBGA84 [DX5001]
S29PL256N60GFI00@FBGA84 [DX5001]
S29PL256N60GFW00@FBGA84 [DX5001]
S29PL256N65GAI00@FBGA84 [DX5001]
S29PL256N65GAW00@FBGA84 [DX5001]
S29PL256N65GAWW0@FBGA84 [DX5001]
S29PL256N65GFI00@FBGA84 [DX5001]
S29PL256N65GFW00@FBGA84 [DX5001]
S29PL256N65GFWW0@FBGA84 [DX5001]
S29PL256N70GAI00@FBGA84 [DX5001]
S29PL256N70GAW00@FBGA84 [DX5001]
S29PL256N70GAWW0@FBGA84 [DX5001]
S29PL256N70GFI00@FBGA84 [DX5001]
S29PL256N70GFW00@FBGA84 [DX5001]
S29PL256N70GFWW0@FBGA84 [DX5001]
S29VS016K0PBJW00@FBGA44 [DX5067]
S29VS016K0PBJW01@FBGA44 [DX5067]
S29VS016KAABJW00@FBGA44 [DX5067]
S29VS016KAABJW01@FBGA44 [DX5067]
S29VS032K0PBJW00@FBGA44 [DX5067]
S29VS032K0PBJW01@FBGA44 [DX5067]
S29VS032KAABJW00@FBGA44 [DX5067]
S29VS032KAABJW01@FBGA44 [DX5067]
S29VS064K0PBJW00@FBGA44 [DX5067]
S29VS064K0PBJW01@FBGA44 [DX5067]
S29VS064KAABJW00@FBGA44 [DX5067]
S29VS064KAABJW01@FBGA44 [DX5067]
S29VS064R0PBHI00@FBGA56 [DX5094]
S29VS064R0PBHI01@FBGA56 [DX5094]
S29VS064R0PBHW00@FBGA56 [DX5094]
S29VS064R0PBHW01@FBGA56 [DX5094]
S29VS064R0SBHI00@FBGA56 [DX5094]
S29VS064R0SBHI01@FBGA56 [DX5094]
S29VS064R0SBHW00@FBGA56 [DX5094]
S29VS064R0SBHW01@FBGA56 [DX5094]
S29VS064RABBHI00@FBGA56 [DX5094]
S29VS064RABBHI01@FBGA56 [DX5094]
S29VS064RABBHW00@FBGA56 [DX5094]
S29VS064RABBHW01@FBGA56 [DX5094]
S29WS064J0PBAI00@FBGA80 [DX5052]
S29WS064J0PBAI01@FBGA80 [DX5052]
S29WS064J0PBAI02@FBGA80 [DX5052]
S29WS064J0PBAI03@FBGA80 [DX5052]
S29WS064J0PBAW00@FBGA80 [DX5052]
S29WS064J0PBAW01@FBGA80 [DX5052]
S29WS064J0PBAW02@FBGA80 [DX5052]
S29WS064J0PBAW03@FBGA80 [DX5052]
S29WS064J0PBFI00@FBGA80 [DX5052]
S29WS064J0PBFI01@FBGA80 [DX5052]
S29WS064J0PBFW00@FBGA80 [DX5052]
S29WS064J0PBFW01@FBGA80 [DX5052]
S29WS064J0SBAI00@FBGA80 [DX5052]
S29WS064J0SBAI01@FBGA80 [DX5052]
S29WS064J0SBAI02@FBGA80 [DX5052]
S29WS064J0SBAI03@FBGA80 [DX5052]
S29WS064J0SBAW00@FBGA80 [DX5052]
S29WS064J0SBAW01@FBGA80 [DX5052]
S29WS064J0SBAW02@FBGA80 [DX5052]
S29WS064J0SBAW03@FBGA80 [DX5052]
S29WS064J0SBFI00@FBGA80 [DX5052]
S29WS064J0SBFI01@FBGA80 [DX5052]

S29WS064J0SBFW00@FBGA80 [DX5052]
S29WS064J0SBFW01@FBGA80 [DX5052]
S29WS064J1ABAI00@FBGA80 [DX5052]
S29WS064J1ABAI01@FBGA80 [DX5052]
S29WS064J1ABAW00@FBGA80 [DX5052]
S29WS064J1ABAW01@FBGA80 [DX5052]
S29WS064R0PBHI00@FBGA84 [DX5001]
S29WS064R0PBHI01@FBGA84 [DX5001]
S29WS064R0PBHW00@FBGA84 [DX5001]
S29WS064R0PBHW01@FBGA84 [DX5001]
S29WS064R0SBHI00@FBGA84 [DX5001]
S29WS064R0SBHI01@FBGA84 [DX5001]
S29WS064R0SBHW00@FBGA84 [DX5001]
S29WS064R0SBHW01@FBGA84 [DX5001]
S29WS064RABBHI00@FBGA84 [DX5001]
S29WS064RABBHI01@FBGA84 [DX5001]
S29WS064RABBHW00@FBGA84 [DX5001]
S29WS064RABBHW01@FBGA84 [DX5001]
S29WS128J0PBAI00@FBGA80 [DX5001]
S29WS128J0PBAI01@FBGA80 [DX5001]
S29WS128J0PBAI02@FBGA80 [DX5001]
S29WS128J0PBAI03@FBGA80 [DX5001]
S29WS128J0PBAI10@FBGA84 [DX5001]
S29WS128J0PBAI11@FBGA84 [DX5001]
S29WS128J0PBAW00@FBGA80 [DX5001]
S29WS128J0PBAW01@FBGA80 [DX5001]
S29WS128J0PBAW02@FBGA80 [DX5001]
S29WS128J0PBAW03@FBGA80 [DX5001]
S29WS128J0PBAW10@FBGA84 [DX5001]
S29WS128J0PBAW11@FBGA84 [DX5001]
S29WS128J0PBFI00@FBGA84 [DX5001]
S29WS128J0PBFI01@FBGA84 [DX5001]
S29WS128J0PBFI10@FBGA84 [DX5001]
S29WS128J0PBFI11@FBGA84 [DX5001]
S29WS128J0PBFW00@FBGA84 [DX5001]
S29WS128J0PBFW01@FBGA84 [DX5001]
S29WS128J0PBFW10@FBGA84 [DX5001]
S29WS128J0PBFW11@FBGA84 [DX5001]
S29WS128J0SBAI00@FBGA80 [DX5001]
S29WS128J0SBAI01@FBGA80 [DX5001]
S29WS128J0SBAI02@FBGA80 [DX5001]
S29WS128J0SBAI03@FBGA80 [DX5001]
S29WS128J0SBAW00@FBGA80 [DX5001]
S29WS128J0SBAW01@FBGA80 [DX5001]
S29WS128J0SBAW02@FBGA80 [DX5001]
S29WS128J0SBAW03@FBGA80 [DX5001]
S29WS128J0SBFI00@FBGA84 [DX5001]
S29WS128J0SBFI01@FBGA84 [DX5001]
S29WS128J0SBFW00@FBGA84 [DX5001]
S29WS128J0SBFW01@FBGA84 [DX5001]
S29WS128J1ABAI00@FBGA80 [DX5001]
S29WS128J1ABAI01@FBGA80 [DX5001]
S29WS128J1ABAW00@FBGA80 [DX5001]
S29WS128J1ABAW01@FBGA80 [DX5001]
S29WS128N0LBAW01@FBGA84 [DX5001]
S29WS128N0LBAW01@FBGA88 [DX5001]
S29WS128N0LBAW11@FBGA84 [DX5001]
S29WS128N0LBAW11@FBGA88 [DX5001]
S29WS128N0LBFW01@FBGA84 [DX5001]
S29WS128N0LBFW01@FBGA88 [DX5001]
S29WS128N0LBFW11@FBGA84 [DX5001]
S29WS128N0LBFW11@FBGA88 [DX5001]
S29WS128N0PBAW01@FBGA84 [DX5001]
S29WS128N0PBAW01@FBGA88 [DX5001]
S29WS128N0PBAW11@FBGA84 [DX5001]
S29WS128N0PBAW11@FBGA88 [DX5001]
S29WS128N0PBFW01@FBGA84 [DX5001]
S29WS128N0PBFW01@FBGA88 [DX5001]
S29WS128N0PBFW11@FBGA84 [DX5001]
S29WS128N0PBFW11@FBGA88 [DX5001]
S29WS128N0SBAW01@FBGA84 [DX5001]
S29WS128N0SBAW01@FBGA88 [DX5001]
S29WS128N0SBAW11@FBGA84 [DX5001]
S29WS128N0SBAW11@FBGA88 [DX5001]
S29WS128N0SBFW01@FBGA84 [DX5001]
S29WS128N0SBFW01@FBGA88 [DX5001]
S29WS128N0SBFW11@FBGA84 [DX5001]
S29WS128N0SBFW11@FBGA88 [DX5001]
S29WS128P0LBAW00@FBGA84 [DX5001]
S29WS128P0LBFW00@FBGA84 [DX5001]
S29WS128P0PBAW00@FBGA84 [DX5001]
S29WS128P0PBFW00@FBGA84 [DX5001]
S29WS128P0SBAW00@FBGA84 [DX5001]
S29WS128P0SBFW00@FBGA84 [DX5001]
S29WS128PABBAW00@FBGA84 [DX5001]
S29WS128PABBFW00@FBGA84 [DX5001]
S29WS128R0LBFW00@FBGA84 [DX5001]
S29WS128R0LBFW20@FBGA84 [DX5001]
S29WS128R0LBFW40@FBGA84 [DX5001]
S29WS128R0LBHW00@FBGA84 [DX5001]
S29WS128R0LBHW20@FBGA84 [DX5001]
S29WS128R0LBHW40@FBGA84 [DX5001]
S29WS128R0PBFW00@FBGA84 [DX5001]
S29WS128R0PBFW20@FBGA84 [DX5001]
S29WS128R0PBFW40@FBGA84 [DX5001]
S29WS128R0PBHW00@FBGA84 [DX5001]

S29WS128R0PBHW20@FBGA84 [DX5001]
S29WS128R0PBHW40@FBGA84 [DX5001]
S29WS128R0SBFW00@FBGA84 [DX5001]
S29WS128R0SBFW20@FBGA84 [DX5001]
S29WS128R0SBFW40@FBGA84 [DX5001]
S29WS128R0SBHW00@FBGA84 [DX5001]
S29WS128R0SBHW20@FBGA84 [DX5001]
S29WS128R0SBHW40@FBGA84 [DX5001]
S29WS128RAABFW00@FBGA84 [DX5001]
S29WS128RAABFW20@FBGA84 [DX5001]
S29WS128RAABFW40@FBGA84 [DX5001]
S29WS128RAABHW00@FBGA84 [DX5001]
S29WS128RAABHW20@FBGA84 [DX5001]
S29WS128RAABHW40@FBGA84 [DX5001]
S29WS128RAGBFW00@FBGA84 [DX5001]
S29WS128RAGBFW20@FBGA84 [DX5001]
S29WS128RAGBFW40@FBGA84 [DX5001]
S29WS128RAGBHW00@FBGA84 [DX5001]
S29WS128RAGBHW20@FBGA84 [DX5001]
S29WS128RAGBHW40@FBGA84 [DX5001]
S29WS256N0LBAW01@FBGA84 [DX5001]
S29WS256N0LBAW11@FBGA84 [DX5001]
S29WS256N0LBFW01@FBGA84 [DX5001]
S29WS256N0LBFW11@FBGA84 [DX5001]
S29WS256N0PBAW01@FBGA84 [DX5001]
S29WS256N0PBAW11@FBGA84 [DX5001]
S29WS256N0PBFW01@FBGA84 [DX5001]
S29WS256N0PBFW11@FBGA84 [DX5001]
S29WS256N0SBAW01@FBGA84 [DX5001]
S29WS256N0SBAW11@FBGA84 [DX5001]
S29WS256N0SBFW01@FBGA84 [DX5001]
S29WS256N0SBFW11@FBGA84 [DX5001]
S29WS256P0LBAW00@FBGA84 [DX5001]
S29WS256P0LBFW00@FBGA84 [DX5001]
S29WS256P0PBAW00@FBGA84 [DX5001]
S29WS256P0PBFW00@FBGA84 [DX5001]
S29WS256P0SBAW00@FBGA84 [DX5001]
S29WS256P0SBFW00@FBGA84 [DX5001]
S29WS256PABBAW00@FBGA84 [DX5001]
S29WS256PABBFW00@FBGA84 [DX5001]
S29WS256R0LBFW00@FBGA84 [DX5001]
S29WS256R0LBFW20@FBGA84 [DX5001]
S29WS256R0LBFW40@FBGA84 [DX5001]
S29WS256R0LBHW00@FBGA84 [DX5001]
S29WS256R0LBHW20@FBGA84 [DX5001]
S29WS256R0LBHW40@FBGA84 [DX5001]
S29WS256R0PBFW00@FBGA84 [DX5001]
S29WS256R0PBFW20@FBGA84 [DX5001]
S29WS256R0PBFW40@FBGA84 [DX5001]
S29WS256R0PBHW00@FBGA84 [DX5001]
S29WS256R0PBHW20@FBGA84 [DX5001]
S29WS256R0PBHW40@FBGA84 [DX5001]
S29WS256R0SBFW00@FBGA84 [DX5001]
S29WS256R0SBFW20@FBGA84 [DX5001]
S29WS256R0SBFW40@FBGA84 [DX5001]
S29WS256R0SBHW00@FBGA84 [DX5001]
S29WS256R0SBHW20@FBGA84 [DX5001]
S29WS256R0SBHW40@FBGA84 [DX5001]
S29WS256RAABFW00@FBGA84 [DX5001]
S29WS256RAABFW20@FBGA84 [DX5001]
S29WS256RAABFW40@FBGA84 [DX5001]
S29WS256RAABHW00@FBGA84 [DX5001]
S29WS256RAABHW20@FBGA84 [DX5001]
S29WS256RAABHW40@FBGA84 [DX5001]
S29WS256RAGBFW00@FBGA84 [DX5001]
S29WS256RAGBFW20@FBGA84 [DX5001]
S29WS256RAGBFW40@FBGA84 [DX5001]
S29WS256RAGBHW00@FBGA84 [DX5001]
S29WS256RAGBHW20@FBGA84 [DX5001]
S29WS256RAGBHW40@FBGA84 [DX5001]
S29WS512P0LBAW00@FBGA84 [DX5001]
S29WS512P0LBFW00@FBGA84 [DX5001]
S29WS512P0PBAW00@FBGA84 [DX5001]
S29WS512P0PBFW00@FBGA84 [DX5001]
S29WS512P0SBAW00@FBGA84 [DX5001]
S29WS512P0SBFW00@FBGA84 [DX5001]
S29WS512PABBAW00@FBGA84 [DX5001]
S29WS512PABBFW00@FBGA84 [DX5001]
S29WS512R0LBFW00@FBGA84 [DX5001]
S29WS512R0LBFW20@FBGA84 [DX5001]
S29WS512R0LBFW40@FBGA84 [DX5001]
S29WS512R0LBHW00@FBGA84 [DX5001]
S29WS512R0LBHW20@FBGA84 [DX5001]
S29WS512R0LBHW40@FBGA84 [DX5001]
S29WS512R0PBFW00@FBGA84 [DX5001]
S29WS512R0PBFW20@FBGA84 [DX5001]
S29WS512R0PBFW40@FBGA84 [DX5001]
S29WS512R0PBHW00@FBGA84 [DX5001]
S29WS512R0PBHW20@FBGA84 [DX5001]
S29WS512R0PBHW40@FBGA84 [DX5001]
S29WS512R0SBFW00@FBGA84 [DX5001]
S29WS512R0SBFW20@FBGA84 [DX5001]
S29WS512R0SBFW40@FBGA84 [DX5001]
S29WS512R0SBHW00@FBGA84 [DX5001]
S29WS512R0SBHW20@FBGA84 [DX5001]
S29WS512R0SBHW40@FBGA84 [DX5001]

S29WS512RAABFW00@FBGA84 [DX5001]
S29WS512RAABFW20@FBGA84 [DX5001]
S29WS512RAABFW40@FBGA84 [DX5001]
S29WS512RAABHW00@FBGA84 [DX5001]
S29WS512RAABHW20@FBGA84 [DX5001]
S29WS512RAABHW40@FBGA84 [DX5001]
S29WS512RAGBFW00@FBGA84 [DX5001]
S29WS512RAGBFW20@FBGA84 [DX5001]
S29WS512RAGBFW40@FBGA84 [DX5001]
S29WS512RAGBHW00@FBGA84 [DX5001]
S29WS512RAGBHW20@FBGA84 [DX5001]
S29WS512RAGBHW40@FBGA84 [DX5001]
S30ML01GP30TFE00@TSOP48 [DX1004]
S30ML01GP30TFE50@TSOP48 [DX1004]
S30ML01GP50TFE01@TSOP48 [DX1004]
S30ML01GP50TFE51@TSOP48 [DX1004]
S30ML02GP30TFE00@TSOP48 [DX1004]
S30ML02GP30TFE50@TSOP48 [DX1004]
S30ML02GP50TFE01@TSOP48 [DX1004]
S30ML02GP50TFE51@TSOP48 [DX1004]
S30ML128P30TFE00@TSOP48 [DX1004]
S30ML128P30TFE50@TSOP48 [DX1004]
S30ML128P50TFE01@TSOP48 [DX1004]
S30ML128P50TFE51@TSOP48 [DX1004]
S30ML256P30TFE00@TSOP48 [DX1004]
S30ML256P30TFE50@TSOP48 [DX1004]
S30ML256P50TFE01@TSOP48 [DX1004]
S30ML256P50TFE51@TSOP48 [DX1004]
S30ML512P30TFI50@TSOP48 [DX1004]
S30ML512P50TFE01@TSOP48 [DX1004]
S30ML512P50TFE51@TSOP48 [DX1004]
S30MS01GP25TFW01@TSOP48 [DX1004]
S30MS01GP25TFW50@TSOP48 [DX1004]
S30MS01GP25TFW51@TSOP48 [DX1004]
S30MS01GR25TFW10@TSOP48 [DX1004]
S30MS01GR25TFW11@TSOP48 [DX1004]
S30MS02GR25TFW01@TSOP48 [DX1004]
S30MS02GR25TFW10@TSOP48 [DX1004]
S30MS512R25TFW10@TSOP48 [DX1004]
S30MS512R25TFW11@TSOP48 [DX1004]
S34ML01G100BHI00@FBGA63 [DX5046]
S34ML01G100TFI00@TSOP48 [DX1004-1]
S34ML01G200BHI00@FBGA63 [DX5046]
S34ML01G200TFI00@TSOP48 [DX1004-1]
S34ML01G204TFI01@TSOP48 [DX1004-1]
S34ML02G100BHI00@FBGA63 [DX5046]
S34ML02G100TFI00@TSOP48 [DX1004-1]
S34ML02G200BHI00@FBGA63 [DX5046]
S34ML02G200TFI00@TSOP48 [DX1004-1]
S34ML04G100BHI00@FBGA63 [DX5046]
S34ML04G100TFI00@TSOP48 [DX1004-1]
S34ML04G200TFI00@TSOP48 [DX1004-1]
S34ML08G101TFI00@TSOP48 [DX1004-3]
S34ML08G201TFI00@TSOP48 [DX1004-1]
S34MS01G200BHI00@FBGA63 [DX5046]
S34MS04G100BHI00@FBGA63 [DX5046]
S34MS04G200BHI00@FBGA63 [DX5046]
S70FL01GS@SOIC16 [DX1033#1]
S70FL01GS@TBGA24 [DX5157]
S70FL01GSAGMxx01 [DX1033#1]
S70FL01GSDPMxx01 [DX1033#1]
S70FL256P@BGA24 [DX5157]
S70FL256P@SOP16 [DX1033#1]
S70FL512P@BGA24 [DX5157]
S70FL512P@SOP16 [DX1033#1]
S70FL512S@BGA24 [DX5157]
S70FL512S@SOP16 [DX1033#1]
S70FS01GS@SOIC16 [DX1033#1]
S70FS01GS@TFBGA24 [DX5157]
S70FS01SAGBxx21 [DX5157]
S70FS01SAGMxx01 [DX1033#1]
S70FS01SAGNxx01 [DX4006#1]
S70GL02GP11FAIR1@FBGA64 [DX5074]
S70GL02GP11FAIR2@FBGA64 [DX5074]
S70GL02GP11FFIR1@FBGA64 [DX5074]
S70GL02GP11FFIR2@FBGA64 [DX5074]
S70GL02GP12FAI01@FBGA64 [DX5074]
S70GL02GP12FAI02@FBGA64 [DX5074]
S70GL02GP12FFI01@FBGA64 [DX5074]
S70GL02GP12FFI02@FBGA64 [DX5074]
S70GL02GP13FAIV1@FBGA64 [DX5074]
S70GL02GP13FAIV2@FBGA64 [DX5074]

S70GL02GP13FFIV1@FBGA64 [DX5074]
S70GL02GP13FFIV2@FBGA64 [DX5074]
S70GL02GS11FHI01@FBGA64 [DX5074]
S70GL02GS11FHI02@FBGA64 [DX5074]
S70GL02GS12FHIV1@FBGA64 [DX5074]
S70GL02GS12FHIV2@FBGA64 [DX5074]
S70PL254J00BAW91@FBGA64 [DX5001]
S70PL254J00BAW93@FBGA64 [DX5001]
S70PL254J00BAWA1@FBGA84 [DX5001]
S70PL254J00BAWA3@FBGA84 [DX5001]
S70PL254J00BFW91@FBGA64 [DX5001]
S70PL254J00BFW93@FBGA64 [DX5001]
S70PL254J00BFWA1@FBGA84 [DX5001]
S70PL254J00BFWA3@FBGA84 [DX5001]
S70PL512N00BAW53@FBGA84 [DX5001]
S70PL512N00BFW53@FBGA84 [DX5001]
S70PL512N00HAW53@FBGA84 [DX5001]
S70PL512N00HFW53@FBGA84 [DX5001]
S71AL016D02BAWB7@FBGA56 [DX5045]
S71AL016D02BAWBF@FBGA56 [DX5045]
S71AL016D02BAWT7@FBGA56 [DX5045]
S71AL016D02BAWTF@FBGA56 [DX5045]
S71AL016D02BFWB7@FBGA56 [DX5045]
S71AL016D02BFWBF@FBGA56 [DX5045]
S71AL016D02BFWT7@FBGA56 [DX5045]
S71AL016D02BFWTF@FBGA56 [DX5045]
S71AL016D04BAWBX@FBGA56 [DX5045]
S71AL016D04BAWTX@FBGA56 [DX5045]
S71AL016D04BFWBX@FBGA56 [DX5045]
S71AL016D04BFWTX@FBGA56 [DX5045]
S71AL016M40BAW0B@FBGA56 [DX5045]
S71AL016M40BAW0F@FBGA56 [DX5045]
S71AL016M40BFW0B@FBGA56 [DX5045]
S71AL016M40BFW0F@FBGA56 [DX5045]
S71GL016A40BAW1J@FBGA56 [DX5045]
S71GL016A40BAW3J@FBGA56 [DX5045]
S71GL016A40BFW1J@FBGA56 [DX5045]
S71GL016A40BFW3J@FBGA56 [DX5045]
S71GL032A08BAW0B@FBGA56 [DX5045]
S71GL032A08BAW0F@FBGA56 [DX5045]
S71GL032A08BFW0B@FBGA56 [DX5045]
S71GL032A08BFW0F@FBGA56 [DX5045]
S71GL032A40BAW0B@FBGA56 [DX5045]
S71GL032A40BAW0F@FBGA56 [DX5045]
S71GL032A40BFW0B@FBGA56 [DX5045]
S71GL032A40BFW0F@FBGA56 [DX5045]
S71GL032A80BAW0K@FBGA56 [DX5045]
S71GL032A80BAW0P@FBGA56 [DX5045]
S71GL032A80BFW0K@FBGA56 [DX5045]
S71GL032A80BFW0P@FBGA56 [DX5045]
S71GL032AA0BAW0U@FBGA56 [DX5045]
S71GL032AA0BAW0Z@FBGA56 [DX5045]
S71GL032AA0BFW0U@FBGA56 [DX5045]
S71GL032AA0BFW0Z@FBGA56 [DX5045]
S71GL032M40BAIBQ@FBGA56 [DX5045]
S71GL032M40BAIFQ@FBGA56 [DX5045]
S71GL032M40BAIKQ@FBGA56 [DX5045]
S71GL032M40BAIPQ@FBGA56 [DX5045]
S71GL032M40BAWBQ@FBGA56 [DX5045]
S71GL032M40BAWFQ@FBGA56 [DX5045]
S71GL032M40BAWKQ@FBGA56 [DX5045]
S71GL032M40BAWPQ@FBGA56 [DX5045]
S71GL032M40BFIBQ@FBGA56 [DX5045]
S71GL032M40BFIFQ@FBGA56 [DX5045]
S71GL032M40BFIKQ@FBGA56 [DX5045]
S71GL032M40BFIPQ@FBGA56 [DX5045]
S71GL032M40BFWBQ@FBGA56 [DX5045]
S71GL032M40BFWFQ@FBGA56 [DX5045]
S71GL032M40BFWKQ@FBGA56 [DX5045]
S71GL032M40BFWPQ@FBGA56 [DX5045]
S71GL032N40BFW0K@FBGA56 [DX5045]
S71GL032N40BFW0P@FBGA56 [DX5045]
S71GL032N40BHW0K@FBGA56 [DX5045]
S71GL032N40BHW0P@FBGA56 [DX5045]
S71GL032N80BFW0K@FBGA56 [DX5045]
S71GL032N80BFW0P@FBGA56 [DX5045]
S71GL032N80BHW0K@FBGA56 [DX5045]
S71GL032N80BHW0P@FBGA56 [DX5045]
S71GL032NA0BFW0U@FBGA56 [DX5045]
S71GL032NA0BFW0Z@FBGA56 [DX5045]
S71GL032NA0BHW0B@FBGA56 [DX5045]
S71GL032NA0BHW0F@FBGA56 [DX5045]
S71GL032NA0BHW0K@FBGA56 [DX5045]
S71GL032NA0BHW0P@FBGA56 [DX5045]
S71GL032NA0BHW0U@FBGA56 [DX5045]
S71GL032NA0BHW0Z@FBGA56 [DX5045]
S71GL064A08BAI0B@FBGA56 [DX5045]
S71GL064A08BAI0F@FBGA56 [DX5045]
S71GL064A08BAW0B@FBGA56 [DX5045]
S71GL064A08BAW0F@FBGA56 [DX5045]
S71GL064A08BFI0B@FBGA56 [DX5045]
S71GL064A08BFI0F@FBGA56 [DX5045]
S71GL064A08BFW0B@FBGA56 [DX5045]
S71GL064A08BFW0F@FBGA56 [DX5045]
S71GL064A0ABAI0B@FBGA56 [DX5045]
S71GL064A0ABAI0F@FBGA56 [DX5045]

S71GL064A0ABAW0B@FBGA56 [DX5045]
S71GL064A0ABAW0F@FBGA56 [DX5045]
S71GL064A0ABFI0B@FBGA56 [DX5045]
S71GL064A0ABFI0F@FBGA56 [DX5045]
S71GL064A0ABFW0B@FBGA56 [DX5045]
S71GL064A0ABFW0F@FBGA56 [DX5045]
S71GL064A80BAI0K@FBGA56 [DX5045]
S71GL064A80BAI0P@FBGA56 [DX5045]
S71GL064A80BAW0K@FBGA56 [DX5045]
S71GL064A80BAW0P@FBGA56 [DX5045]
S71GL064A80BFI0K@FBGA56 [DX5045]
S71GL064A80BFI0P@FBGA56 [DX5045]
S71GL064A80BFW0K@FBGA56 [DX5045]
S71GL064A80BFW0P@FBGA56 [DX5045]
S71GL064AA0BAI0K@FBGA56 [DX5045]
S71GL064AA0BAI0P@FBGA56 [DX5045]
S71GL064AA0BAI0U@FBGA56 [DX5045]
S71GL064AA0BAI0Z@FBGA56 [DX5045]
S71GL064AA0BAW0K@FBGA56 [DX5045]
S71GL064AA0BAW0P@FBGA56 [DX5045]
S71GL064AA0BAW0U@FBGA56 [DX5045]
S71GL064AA0BAW0Z@FBGA56 [DX5045]
S71GL064AA0BFI0K@FBGA56 [DX5045]
S71GL064AA0BFI0P@FBGA56 [DX5045]
S71GL064AA0BFI0U@FBGA56 [DX5045]
S71GL064AA0BFI0Z@FBGA56 [DX5045]
S71GL064AA0BFW0K@FBGA56 [DX5045]
S71GL064AA0BFW0P@FBGA56 [DX5045]
S71GL064AA0BFW0U@FBGA56 [DX5045]
S71GL064AA0BFW0Z@FBGA56 [DX5045]
S71GL064AB0BAI0U@FBGA56 [DX5045]
S71GL064AB0BAI0Z@FBGA56 [DX5045]
S71GL064AB0BAW0U@FBGA56 [DX5045]
S71GL064AB0BAW0Z@FBGA56 [DX5045]
S71GL064AB0BFI0U@FBGA56 [DX5045]
S71GL064AB0BFI0Z@FBGA56 [DX5045]
S71GL064AB0BFW0U@FBGA56 [DX5045]
S71GL064AB0BFW0Z@FBGA56 [DX5045]
S71GL064NA0BFW0U@FBGA56 [DX5045]
S71GL064NA0BFW0Z@FBGA56 [DX5045]
S71GL064NA0BHW0B@FBGA56 [DX5045]
S71GL064NA0BHW0F@FBGA56 [DX5045]
S71GL064NA0BHW0U@FBGA56 [DX5045]
S71GL064NA0BHW0Z@FBGA56 [DX5045]
S71GL064NB0BFW0K@FBGA56 [DX5045]
S71GL064NB0BFW0P@FBGA56 [DX5045]
S71GL064NB0BFW0U@FBGA56 [DX5045]
S71GL064NB0BFW0Z@FBGA56 [DX5045]
S71GL064NB0BHW0K@FBGA56 [DX5045]
S71GL064NB0BHW0P@FBGA56 [DX5045]
S71GL064NB0BHW0U@FBGA56 [DX5045]
S71GL064NB0BHW0Z@FBGA56 [DX5045]
S71GL128NB0BAEAT@FBGA84 [DX5001]
S71GL128NB0BAEAU@FBGA84 [DX5001]
S71GL128NB0BAEAY@FBGA84 [DX5001]
S71GL128NB0BAEAZ@FBGA84 [DX5001]
S71GL128NB0BAW9J@FBGA64 [DX5001]
S71GL128NB0BAW9K@FBGA64 [DX5001]
S71GL128NB0BAW9N@FBGA64 [DX5001]
S71GL128NB0BAW9P@FBGA64 [DX5001]
S71GL128NB0BAW9T@FBGA64 [DX5001]
S71GL128NB0BAW9U@FBGA64 [DX5001]
S71GL128NB0BAW9Y@FBGA64 [DX5001]
S71GL128NB0BAW9Z@FBGA64 [DX5001]
S71GL128NB0BAWAJ@FBGA84 [DX5001]
S71GL128NB0BAWAK@FBGA84 [DX5001]
S71GL128NB0BAWAN@FBGA84 [DX5001]
S71GL128NB0BAWAP@FBGA84 [DX5001]
S71GL128NB0BAWAT@FBGA84 [DX5001]
S71GL128NB0BAWAU@FBGA84 [DX5001]
S71GL128NB0BAWAY@FBGA84 [DX5001]
S71GL128NB0BAWAZ@FBGA84 [DX5001]
S71GL128NB0BAWEJ@FBGA84 [DX5001]
S71GL128NB0BAWEK@FBGA84 [DX5001]
S71GL128NB0BAWEN@FBGA84 [DX5001]
S71GL128NB0BAWEP@FBGA84 [DX5001]
S71GL128NB0BAWET@FBGA84 [DX5001]
S71GL128NB0BAWEU@FBGA84 [DX5001]
S71GL128NB0BAWEY@FBGA84 [DX5001]
S71GL128NB0BAWEZ@FBGA84 [DX5001]
S71GL128NB0BFEAT@FBGA84 [DX5001]
S71GL128NB0BFEAU@FBGA84 [DX5001]
S71GL128NB0BFEAY@FBGA84 [DX5001]
S71GL128NB0BFEAZ@FBGA84 [DX5001]
S71GL128NB0BFW9J@FBGA64 [DX5001]
S71GL128NB0BFW9K@FBGA64 [DX5001]
S71GL128NB0BFW9N@FBGA64 [DX5001]
S71GL128NB0BFW9P@FBGA64 [DX5001]
S71GL128NB0BFW9T@FBGA64 [DX5001]
S71GL128NB0BFW9U@FBGA64 [DX5001]
S71GL128NB0BFW9Y@FBGA64 [DX5001]
S71GL128NB0BFW9Z@FBGA64 [DX5001]
S71GL128NB0BFWAJ@FBGA84 [DX5001]
S71GL128NB0BFWAK@FBGA84 [DX5001]
S71GL128NB0BFWAN@FBGA84 [DX5001]
S71GL128NB0BFWAP@FBGA84 [DX5001]

S71GL128NB0BFWAT@FBGA84 [DX5001]
S71GL128NB0BFWAU@FBGA84 [DX5001]
S71GL128NB0BFWAY@FBGA84 [DX5001]
S71GL128NB0BFWAZ@FBGA84 [DX5001]
S71GL128NB0BFWEJ@FBGA84 [DX5001]
S71GL128NB0BFWEK@FBGA84 [DX5001]
S71GL128NB0BFWEN@FBGA84 [DX5001]
S71GL128NB0BFWEP@FBGA84 [DX5001]
S71GL128NB0BFWET@FBGA84 [DX5001]
S71GL128NB0BFWEU@FBGA84 [DX5001]
S71GL128NB0BFWEY@FBGA84 [DX5001]
S71GL128NB0BFWEZ@FBGA84 [DX5001]
S71GL128NC0BAEAT@FBGA84 [DX5001]
S71GL128NC0BAEAU@FBGA84 [DX5001]
S71GL128NC0BAEAY@FBGA84 [DX5001]
S71GL128NC0BAWAT@FBGA84 [DX5001]
S71GL128NC0BAWAU@FBGA84 [DX5001]
S71GL128NC0BAWAY@FBGA84 [DX5001]
S71GL128NC0BAWAZ@FBGA84 [DX5001]
S71GL128NC0BAZAY@FBGA84 [DX5001]
S71GL128NC0BFEAT@FBGA84 [DX5001]
S71GL128NC0BFEAU@FBGA84 [DX5001]
S71GL128NC0BFEAY@FBGA84 [DX5001]
S71GL128NC0BFEAZ@FBGA84 [DX5001]
S71GL128NC0BFWAT@FBGA84 [DX5001]
S71GL128NC0BFWAU@FBGA84 [DX5001]
S71GL128NC0BFWAY@FBGA84 [DX5001]
S71GL128NC0BFWAZ@FBGA84 [DX5001]
S71GL128PC0HH30Y@FBGA84 [DX5001]
S71GL128PC0HH31Y@FBGA84 [DX5001]
S71GL256NB0BAWAJ@FBGA84 [DX5001]
S71GL256NB0BAWAK@FBGA84 [DX5001]
S71GL256NB0BAWAN@FBGA84 [DX5001]
S71GL256NB0BAWAP@FBGA84 [DX5001]
S71GL256NB0BAWAT@FBGA84 [DX5001]
S71GL256NB0BAWAU@FBGA84 [DX5001]
S71GL256NB0BAWAY@FBGA84 [DX5001]
S71GL256NB0BAWAZ@FBGA84 [DX5001]
S71GL256NB0BAWEJ@FBGA84 [DX5001]
S71GL256NB0BAWEK@FBGA84 [DX5001]
S71GL256NB0BAWEN@FBGA84 [DX5001]
S71GL256NB0BAWEP@FBGA84 [DX5001]
S71GL256NB0BAWET@FBGA84 [DX5001]
S71GL256NB0BAWEU@FBGA84 [DX5001]
S71GL256NB0BAWEY@FBGA84 [DX5001]
S71GL256NB0BAWEZ@FBGA84 [DX5001]
S71GL256NB0BFWAJ@FBGA84 [DX5001]
S71GL256NB0BFWAK@FBGA84 [DX5001]
S71GL256NB0BFWAN@FBGA84 [DX5001]
S71GL256NB0BFWAP@FBGA84 [DX5001]
S71GL256NB0BFWAT@FBGA84 [DX5001]
S71GL256NB0BFWAU@FBGA84 [DX5001]
S71GL256NB0BFWAY@FBGA84 [DX5001]
S71GL256NB0BFWAZ@FBGA84 [DX5001]
S71GL256NB0BFWEJ@FBGA84 [DX5001]
S71GL256NB0BFWEK@FBGA84 [DX5001]
S71GL256NB0BFWEN@FBGA84 [DX5001]
S71GL256NB0BFWEP@FBGA84 [DX5001]
S71GL256NB0BFWET@FBGA84 [DX5001]
S71GL256NB0BFWEU@FBGA84 [DX5001]
S71GL256NB0BFWEY@FBGA84 [DX5001]
S71GL256NB0BFWEZ@FBGA84 [DX5001]
S71GL256NC0BAEAT@FBGA84 [DX5001]
S71GL256NC0BAEAU@FBGA84 [DX5001]
S71GL256NC0BAEAY@FBGA84 [DX5001]
S71GL256NC0BAEAZ@FBGA84 [DX5001]
S71GL256NC0BAWAT@FBGA84 [DX5001]
S71GL256NC0BAWAU@FBGA84 [DX5001]
S71GL256NC0BAWAY@FBGA84 [DX5001]
S71GL256NC0BAWAZ@FBGA84 [DX5001]
S71GL256NC0BFEAT@FBGA84 [DX5001]
S71GL256NC0BFEAU@FBGA84 [DX5001]
S71GL256NC0BFEAY@FBGA84 [DX5001]
S71GL256NC0BFEAZ@FBGA84 [DX5001]
S71GL256NC0BFWAT@FBGA84 [DX5001]
S71GL256NC0BFWAU@FBGA84 [DX5001]
S71GL256NC0BFWAY@FBGA84 [DX5001]
S71GL256NC0BFWAZ@FBGA84 [DX5001]
S71GL512NB0BAWEJ@FBGA84 [DX5054]
S71GL512NB0BAWEK@FBGA84 [DX5054]
S71GL512NB0BAWEN@FBGA84 [DX5054]
S71GL512NB0BAWEP@FBGA84 [DX5054]
S71GL512NB0BAWET@FBGA84 [DX5054]
S71GL512NB0BAWEU@FBGA84 [DX5054]
S71GL512NB0BAWEY@FBGA84 [DX5054]
S71GL512NB0BAWEZ@FBGA84 [DX5054]
S71GL512NB0BFWEJ@FBGA84 [DX5054]
S71GL512NB0BFWEK@FBGA84 [DX5054]
S71GL512NB0BFWEN@FBGA84 [DX5054]
S71GL512NB0BFWEP@FBGA84 [DX5054]
S71GL512NB0BFWET@FBGA84 [DX5054]
S71GL512NB0BFWEU@FBGA84 [DX5054]
S71GL512NB0BFWEY@FBGA84 [DX5054]
S71GL512NB0BFWEZ@FBGA84 [DX5054]
S71GL512NC0BAWET@FBGA84 [DX5054]
S71GL512NC0BAWEU@FBGA84 [DX5054]

S71GL512NC0BAWEY@FBGA84 [DX5054]
S71GL512NC0BAWEZ@FBGA84 [DX5054]
S71GL512NC0BFWET@FBGA84 [DX5054]
S71GL512NC0BFWEU@FBGA84 [DX5054]
S71GL512NC0BFWEY@FBGA84 [DX5054]
S71GL512NC0BFWEZ@FBGA84 [DX5054]
S71JL064H80BAI01@FBGA73 [DX5001]
S71JL064H80BAI02@FBGA73 [DX5001]
S71JL064H80BAI10@FBGA73 [DX5001]
S71JL064H80BAI11@FBGA73 [DX5001]
S71JL064H80BAI12@FBGA73 [DX5001]
S71JL064H80BAW01@FBGA73 [DX5001]
S71JL064H80BAW02@FBGA73 [DX5001]
S71JL064H80BAW03@FBGA73 [DX5001]
S71JL064H80BAW04@FBGA73 [DX5001]
S71JL064H80BAW10@FBGA73 [DX5001]
S71JL064H80BAW11@FBGA73 [DX5001]
S71JL064H80BAW12@FBGA73 [DX5001]
S71JL064H80BFI01@FBGA73 [DX5001]
S71JL064H80BFI02@FBGA73 [DX5001]
S71JL064H80BFI10@FBGA73 [DX5001]
S71JL064H80BFI11@FBGA73 [DX5001]
S71JL064H80BFI12@FBGA73 [DX5001]
S71JL064H80BFW01@FBGA73 [DX5001]
S71JL064H80BFW02@FBGA73 [DX5001]
S71JL064H80BFW10@FBGA73 [DX5001]
S71JL064H80BFW11@FBGA73 [DX5001]
S71JL064H80BFW12@FBGA73 [DX5001]
S71JL064HA0BAI01@FBGA73 [DX5001]
S71JL064HA0BAI02@FBGA73 [DX5001]
S71JL064HA0BAI10@FBGA73 [DX5001]
S71JL064HA0BAI11@FBGA73 [DX5001]
S71JL064HA0BAI12@FBGA73 [DX5001]
S71JL064HA0BAI62@FBGA73 [DX5001]
S71JL064HA0BAW01@FBGA73 [DX5001]
S71JL064HA0BAW02@FBGA73 [DX5001]
S71JL064HA0BAW10@FBGA73 [DX5001]
S71JL064HA0BAW11@FBGA73 [DX5001]
S71JL064HA0BAW12@FBGA73 [DX5001]
S71JL064HA0BAW62@FBGA73 [DX5001]
S71JL064HA0BFI01@FBGA73 [DX5001]
S71JL064HA0BFI02@FBGA73 [DX5001]
S71JL064HA0BFI10@FBGA73 [DX5001]
S71JL064HA0BFI11@FBGA73 [DX5001]
S71JL064HA0BFI12@FBGA73 [DX5001]
S71JL064HA0BFI62@FBGA73 [DX5001]
S71JL064HA0BFW01@FBGA73 [DX5001]
S71JL064HA0BFW02@FBGA73 [DX5001]
S71JL064HA0BFW10@FBGA73 [DX5001]
S71JL064HA0BFW11@FBGA73 [DX5001]
S71JL064HA0BFW12@FBGA73 [DX5001]
S71JL064HA0BFW62@FBGA73 [DX5001]
S71JL064HB0BAI00@FBGA73 [DX5001]
S71JL064HB0BAI01@FBGA73 [DX5001]
S71JL064HB0BAI02@FBGA73 [DX5001]
S71JL064HB0BAW00@FBGA73 [DX5001]
S71JL064HB0BAW01@FBGA73 [DX5001]
S71JL064HB0BAW02@FBGA73 [DX5001]
S71JL064HB0BFI00@FBGA73 [DX5001]
S71JL064HB0BFI01@FBGA73 [DX5001]
S71JL064HB0BFI02@FBGA73 [DX5001]
S71JL064HB0BFW00@FBGA73 [DX5001]
S71JL064HB0BFW01@FBGA73 [DX5001]
S71JL064HB0BFW02@FBGA73 [DX5001]
S71JL128HB0BAI00@FBGA73 [DX5001]
S71JL128HB0BAI01@FBGA73 [DX5001]
S71JL128HB0BAI02@FBGA73 [DX5001]
S71JL128HB0BAI03@FBGA73 [DX5001]
S71JL128HB0BAW00@FBGA73 [DX5001]
S71JL128HB0BAW01@FBGA73 [DX5001]
S71JL128HB0BAW02@FBGA73 [DX5001]
S71JL128HB0BAW03@FBGA73 [DX5001]
S71JL128HB0BFI00@FBGA73 [DX5001]
S71JL128HB0BFI01@FBGA73 [DX5001]
S71JL128HB0BFI02@FBGA73 [DX5001]
S71JL128HB0BFI03@FBGA73 [DX5001]
S71JL128HB0BFW00@FBGA73 [DX5001]
S71JL128HB0BFW01@FBGA73 [DX5001]
S71JL128HB0BFW02@FBGA73 [DX5001]
S71JL128HB0BFW03@FBGA73 [DX5001]
S71JL128HC0BAI00@FBGA88 [DX5001]
S71JL128HC0BAI01@FBGA88 [DX5001]
S71JL128HC0BAI02@FBGA88 [DX5001]
S71JL128HC0BAI03@FBGA88 [DX5001]
S71JL128HC0BAW00@FBGA88 [DX5001]
S71JL128HC0BAW01@FBGA88 [DX5001]
S71JL128HC0BAW02@FBGA88 [DX5001]
S71JL128HC0BAW03@FBGA88 [DX5001]
S71JL128HC0BFI00@FBGA88 [DX5001]
S71JL128HC0BFI01@FBGA88 [DX5001]
S71JL128HC0BFI02@FBGA88 [DX5001]
S71JL128HC0BFI03@FBGA88 [DX5001]
S71JL128HC0BFW00@FBGA88 [DX5001]
S71JL128HC0BFW01@FBGA88 [DX5001]
S71JL128HC0BFW02@FBGA88 [DX5001]
S71JL128HC0BFW03@FBGA88 [DX5001]

S71NS032J80BJWRA@FBGA56 [DX5066]
S71NS032J80BJWU6@FBGA56 [DX5066]
S71NS032JA0BJWRA@FBGA56 [DX5066]
S71NS032JA0BJWRT@FBGA56 [DX5066]
S71NS032JA0BJWUN@FBGA56 [DX5066]
S71NS064JA0BAW01@FBGA44 [DX5066]
S71NS064JA0BAW11@FBGA44 [DX5066]
S71NS064JA0BAW21@FBGA44 [DX5066]
S71NS064JA0BFW01@FBGA44 [DX5066]
S71NS064JA0BFW11@FBGA44 [DX5066]
S71NS064JA0BFW21@FBGA44 [DX5066]
S71NS064JA0BJWRN@FBGA56 [DX5066]
S71NS064N80BHWRA@FBGA56 [DX5066]
S71NS064N80BJWRA@FBGA56 [DX5066]
S71NS064NA0BHWRA@FBGA56 [DX5066]
S71NS064NA0BHWRN@FBGA56 [DX5066]
S71NS064NA0BJWRA@FBGA56 [DX5066]
S71NS064NA0BJWRN@FBGA56 [DX5066]
S71NS064NB0BHWUN@FBGA56 [DX5066]
S71NS064NB0BJWUN@FBGA56 [DX5066]
S71NS128JA0BAW01@FBGA48 [DX50UN]
S71NS128JA0BAW11@FBGA48 [DX50UN]
S71NS128JA0BAW21@FBGA48 [DX50UN]
S71NS128JA0BFW01@FBGA48 [DX50UN]
S71NS128JA0BFW11@FBGA48 [DX50UN]
S71NS128JA0BFW21@FBGA48 [DX50UN]
S71NS128NA0BJWRN@FBGA56 [DX5066]
S71NS128NA0BJWSN@FBGA44 [DX5066]
S71NS128NB0BJWRN@FBGA56 [DX5066]
S71NS128NC0BJWRN@FBGA56 [DX5066]
S71NS128PA0ZJAGV@FBGA44 [DX5067]
S71NS128PB0ZJEJR@FBGA56 [DX5066]
S71NS128PB0ZJETV@FBGA56 [DX5066]
S71NS128PB0ZJETZ@FBGA56 [DX5183]
S71NS128PC0ZJEJR@FBGA56 [DX5066]
S71NS128PC0ZJETV@FBGA56 [DX5066]
S71NS128RA0AHAGR@FBGA44 [DX5067]
S71NS128RA0AHAGV@FBGA44 [DX5067]
S71NS128RA0AHAJR@FBGA44 [DX5067]
S71NS128RA0AHAJV@FBGA44 [DX5067]
S71NS128RA0ZHAGR@FBGA44 [DX5067]
S71NS128RA0ZHAGV@FBGA44 [DX5067]
S71NS128RA0ZHAJR@FBGA44 [DX5067]
S71NS128RA0ZHAJV@FBGA44 [DX5067]
S71NS256NB0BJWVN@FBGA60 [DX50UN]
S71NS256NC0BJWVN@FBGA60 [DX50UN]
S71NS256PB0ZJEJR@FBGA56 [DX5066]
S71NS256PB0ZJETV@FBGA56 [DX5066]
S71NS256PC0ZJEJR@FBGA56 [DX5066]
S71NS256PC0ZJETV@FBGA56 [DX5066]
S71NS256RB0AHAGR@FBGA44 [DX5067]
S71NS256RB0AHAGV@FBGA44 [DX5067]
S71NS256RB0AHAJR@FBGA44 [DX5067]
S71NS256RB0AHAJV@FBGA44 [DX5067]
S71NS256RB0ZHAGR@FBGA44 [DX5067]
S71NS256RB0ZHAGV@FBGA44 [DX5067]
S71NS256RB0ZHAJR@FBGA44 [DX5067]
S71NS256RB0ZHAJV@FBGA44 [DX5067]
S71NS256RC0ZHKJL@FBGA56 [DX5067]
S71NS256RD0ZHEJL@FBGA56 [DX5066]
S71NS512RD0ZHEJL@FBGA56 [DX5066]
S71NS512RD0ZHEKL@FBGA56 [DX5066]
S71NS512RD0ZHEKL@FBGA56(HW) [DX5066]
S71NS512RD0ZHEML@FBGA56 [DX5066]
S71PL032J04BAI0B@FBGA56 [DX5045]
S71PL032J04BAI0F@FBGA56 [DX5045]
S71PL032J04BAW0B@FBGA56 [DX5045]
S71PL032J04BAW0F@FBGA56 [DX5045]
S71PL032J04BAW0K@FBGA56 [DX5045]
S71PL032J04BFI0B@FBGA56 [DX5045]
S71PL032J04BFI0F@FBGA56 [DX5045]
S71PL032J04BFW0B@FBGA56 [DX5045]
S71PL032J04BFW0F@FBGA56 [DX5045]
S71PL032J04BFW0K@FBGA56 [DX5045]
S71PL032J08BAE0B@FBGA56 [DX5045]
S71PL032J08BAI07@FBGA56 [DX5045]
S71PL032J08BAW07@FBGA56 [DX5045]
S71PL032J08BAW0B@FBGA56 [DX5045]
S71PL032J08BAW0K@FBGA56 [DX5045]
S71PL032J08BFE0B@FBGA56 [DX5045]
S71PL032J08BFI07@FBGA56 [DX5045]
S71PL032J08BFW07@FBGA56 [DX5045]
S71PL032J08BFW0B@FBGA56 [DX5045]
S71PL032J08BFW0K@FBGA56 [DX5045]
S71PL032J40BAI07@FBGA56 [DX5045]
S71PL032J40BAW07@FBGA56 [DX5045]
S71PL032J40BFI07@FBGA56 [DX5045]
S71PL032J40BFW07@FBGA56 [DX5045]
S71PL032J80BAI05@FBGA56 [DX5045]
S71PL032J80BAI07@FBGA56 [DX5045]
S71PL032J80BAW05@FBGA56 [DX5045]
S71PL032J80BAW07@FBGA56 [DX5045]
S71PL032J80BAW0P@FBGA56 [DX5045]
S71PL032J80BAWQ7@FBGA56 [DX5045]
S71PL032J80BAWQF@FBGA56 [DX5045]

S71PL032J80BFI05@FBGA56 [DX5045]
S71PL032J80BFI07@FBGA56 [DX5045]
S71PL032J80BFW05@FBGA56 [DX5045]
S71PL032J80BFW07@FBGA56 [DX5045]
S71PL032J80BFW0P@FBGA56 [DX5045]
S71PL032J80BFWQ7@FBGA56 [DX5045]
S71PL032J80BFWQF@FBGA56 [DX5045]
S71PL032JA0BAE07@FBGA56 [DX5045]
S71PL032JA0BAE0F@FBGA56 [DX5045]
S71PL032JA0BAI07@FBGA56 [DX5045]
S71PL032JA0BAI0F@FBGA56 [DX5045]
S71PL032JA0BAW07@FBGA56 [DX5045]
S71PL032JA0BAW0F@FBGA56 [DX5045]
S71PL032JA0BAW0Z@FBGA56 [DX5045]
S71PL032JA0BAWQF@FBGA56 [DX5045]
S71PL032JA0BFE07@FBGA56 [DX5045]
S71PL032JA0BFE0F@FBGA56 [DX5045]
S71PL032JA0BFI07@FBGA56 [DX5045]
S71PL032JA0BFI0F@FBGA56 [DX5045]
S71PL032JA0BFW07@FBGA56 [DX5045]
S71PL032JA0BFW0F@FBGA56 [DX5045]
S71PL032JA0BFW0Z@FBGA56 [DX5045]
S71PL032JA0BFWQF@FBGA56 [DX5045]
S71PL064J08BAI0B@FBGA56 [DX5045]
S71PL064J08BAI0K@FBGA56 [DX5045]
S71PL064J08BAI0P@FBGA56 [DX5045]
S71PL064J08BAI0U@FBGA56 [DX5045]
S71PL064J08BAW0B@FBGA56 [DX5045]
S71PL064J08BAW0K@FBGA56 [DX5045]
S71PL064J08BAW0P@FBGA56 [DX5045]
S71PL064J08BAW0U@FBGA56 [DX5045]
S71PL064J08BFI0B@FBGA56 [DX5045]
S71PL064J08BFI0K@FBGA56 [DX5045]
S71PL064J08BFI0P@FBGA56 [DX5045]
S71PL064J08BFI0U@FBGA56 [DX5045]
S71PL064J08BFW0B@FBGA56 [DX5045]
S71PL064J08BFW0K@FBGA56 [DX5045]
S71PL064J08BFW0P@FBGA56 [DX5045]
S71PL064J08BFW0U@FBGA56 [DX5045]
S71PL064J0ABAW0B@FBGA56 [DX5045]
S71PL064J0ABAW0S@FBGA56 [DX5045]
S71PL064J0ABFW0B@FBGA56 [DX5045]
S71PL064J0ABFW0S@FBGA56 [DX5045]
S71PL064J80BAI05@FBGA56 [DX5045]
S71PL064J80BAI07@FBGA56 [DX5045]
S71PL064J80BAI0K@FBGA56 [DX5045]
S71PL064J80BAW05@FBGA56 [DX5045]
S71PL064J80BAW07@FBGA56 [DX5045]
S71PL064J80BAW0K@FBGA56 [DX5045]
S71PL064J80BAW0P@FBGA56 [DX5045]
S71PL064J80BFI05@FBGA56 [DX5045]
S71PL064J80BFI07@FBGA56 [DX5045]
S71PL064J80BFI0K@FBGA56 [DX5045]
S71PL064J80BFW05@FBGA56 [DX5045]
S71PL064J80BFW07@FBGA56 [DX5045]
S71PL064J80BFW0K@FBGA56 [DX5045]
S71PL064J80BFW0P@FBGA56 [DX5045]
S71PL064JA0BAI05@FBGA56 [DX5045]
S71PL064JA0BAI07@FBGA56 [DX5045]
S71PL064JA0BAI0P@FBGA56 [DX5045]
S71PL064JA0BAI0Z@FBGA56 [DX5045]
S71PL064JA0BAW05@FBGA56 [DX5045]
S71PL064JA0BAW07@FBGA56 [DX5045]
S71PL064JA0BAW0B@FBGA56 [DX5045]
S71PL064JA0BAW0P@FBGA56 [DX5045]
S71PL064JA0BAW0Z@FBGA56 [DX5045]
S71PL064JA0BFI05@FBGA56 [DX5045]
S71PL064JA0BFI07@FBGA56 [DX5045]
S71PL064JA0BFI0P@FBGA56 [DX5045]
S71PL064JA0BFI0Z@FBGA56 [DX5045]
S71PL064JA0BFW05@FBGA56 [DX5045]
S71PL064JA0BFW07@FBGA56 [DX5045]
S71PL064JA0BFW0B@FBGA56 [DX5045]
S71PL064JA0BFW0P@FBGA56 [DX5045]
S71PL064JA0BFW0Z@FBGA56 [DX5045]
S71PL064JB0BAI07@FBGA56 [DX5045]
S71PL064JB0BAI0U@FBGA56 [DX5045]
S71PL064JB0BAIQB@FBGA56 [DX5045]
S71PL064JB0BAW07@FBGA56 [DX5045]
S71PL064JB0BAW0B@FBGA56 [DX5045]
S71PL064JB0BAW0U@FBGA56 [DX5045]
S71PL064JB0BAWQB@FBGA56 [DX5045]
S71PL064JB0BFI07@FBGA56 [DX5045]
S71PL064JB0BFI0U@FBGA56 [DX5045]
S71PL064JB0BFIQB@FBGA56 [DX5045]
S71PL064JB0BFW07@FBGA56 [DX5045]
S71PL064JB0BFW0B@FBGA56 [DX5045]
S71PL064JB0BFW0U@FBGA56 [DX5045]
S71PL064JB0BFWQB@FBGA56 [DX5045]
S71PL127JA0BAI9P@FBGA64 [DX5001]
S71PL127JA0BAI9Z@FBGA64 [DX5001]
S71PL127JA0BAW9P@FBGA64 [DX5001]
S71PL127JA0BAW9Z@FBGA64 [DX5001]
S71PL127JA0BFI9P@FBGA64 [DX5001]
S71PL127JA0BFI9Z@FBGA64 [DX5001]
S71PL127JA0BFW9P@FBGA64 [DX5001]

S71PL127JA0BFW9Z@FBGA64 [DX5001]
S71PL127JB0BAI97@FBGA64 [DX5001]
S71PL127JB0BAI9U@FBGA64 [DX5001]
S71PL127JB0BAI9Z@FBGA64 [DX5001]
S71PL127JB0BAIQB@FBGA64 [DX5001]
S71PL127JB0BAW97@FBGA64 [DX5001]
S71PL127JB0BAW9B@FBGA64 [DX5001]
S71PL127JB0BAW9U@FBGA64 [DX5001]
S71PL127JB0BAW9Z@FBGA64 [DX5001]
S71PL127JB0BAWQB@FBGA64 [DX5001]
S71PL127JB0BFI97@FBGA64 [DX5001]
S71PL127JB0BFI9U@FBGA64 [DX5001]
S71PL127JB0BFI9Z@FBGA64 [DX5001]
S71PL127JB0BFIQB@FBGA64 [DX5001]
S71PL127JB0BFW97@FBGA64 [DX5001]
S71PL127JB0BFW9B@FBGA64 [DX5001]
S71PL127JB0BFW9U@FBGA64 [DX5001]
S71PL127JB0BFW9Z@FBGA64 [DX5001]
S71PL127JB0BFWQB@FBGA64 [DX5001]
S71PL127JC0BAI97@FBGA64 [DX5001]
S71PL127JC0BAI9U@FBGA64 [DX5001]
S71PL127JC0BAI9Z@FBGA64 [DX5001]
S71PL127JC0BAW97@FBGA64 [DX5001]
S71PL127JC0BAW9B@FBGA64 [DX5001]
S71PL127JC0BAW9U@FBGA64 [DX5001]
S71PL127JC0BAW9Z@FBGA64 [DX5001]
S71PL127JC0BFI97@FBGA64 [DX5001]
S71PL127JC0BFI9U@FBGA64 [DX5001]
S71PL127JC0BFI9Z@FBGA64 [DX5001]
S71PL127JC0BFW97@FBGA64 [DX5001]
S71PL127JC0BFW9B@FBGA64 [DX5001]
S71PL127JC0BFW9U@FBGA64 [DX5001]
S71PL127JC0BFW9Z@FBGA64 [DX5001]
S71PL127NB0HAW4B@FBGA64 [DX5001]
S71PL127NB0HAW4U@FBGA64 [DX5001]
S71PL127NB0HAW4Z@FBGA64 [DX5001]
S71PL127NB0HFW4B@FBGA64 [DX5001]
S71PL127NB0HFW4U@FBGA64 [DX5001]
S71PL127NB0HFW4Z@FBGA64 [DX5001]
S71PL127NB0HHW4U@FBGA64 [DX5001]
S71PL127NC0HAW4B@FBGA64 [DX5001]
S71PL127NC0HAW4U@FBGA64 [DX5001]
S71PL127NC0HFW4B@FBGA64 [DX5001]
S71PL127NC0HFW4U@FBGA64 [DX5001]
S71PL129JA0BAI9P@FBGA64 [DX5001]
S71PL129JA0BAW9P@FBGA64 [DX5001]
S71PL129JA0BFI9P@FBGA64 [DX5001]
S71PL129JA0BFW9P@FBGA64 [DX5001]
S71PL129JB0BAI9B@FBGA64 [DX5001]
S71PL129JB0BAI9U@FBGA64 [DX5001]
S71PL129JB0BAI9Z@FBGA64 [DX5001]
S71PL129JB0BAIQB@FBGA64 [DX5001]
S71PL129JB0BAIQU@FBGA64 [DX5001]
S71PL129JB0BAIQZ@FBGA64 [DX5001]
S71PL129JB0BAW9B@FBGA64 [DX5001]
S71PL129JB0BAW9P@FBGA64 [DX5001]
S71PL129JB0BAW9U@FBGA64 [DX5001]
S71PL129JB0BAW9Z@FBGA64 [DX5001]
S71PL129JB0BAWQB@FBGA64 [DX5001]
S71PL129JB0BAWQU@FBGA64 [DX5001]
S71PL129JB0BAWQZ@FBGA64 [DX5001]
S71PL129JB0BFI9B@FBGA64 [DX5001]
S71PL129JB0BFI9U@FBGA64 [DX5001]
S71PL129JB0BFI9Z@FBGA64 [DX5001]
S71PL129JB0BFIQB@FBGA64 [DX5001]
S71PL129JB0BFIQU@FBGA64 [DX5001]
S71PL129JB0BFIQZ@FBGA64 [DX5001]
S71PL129JB0BFW9B@FBGA64 [DX5001]
S71PL129JB0BFW9P@FBGA64 [DX5001]
S71PL129JB0BFW9U@FBGA64 [DX5001]
S71PL129JB0BFW9Z@FBGA64 [DX5001]
S71PL129JB0BFWQB@FBGA64 [DX5001]
S71PL129JB0BFWQU@FBGA64 [DX5001]
S71PL129JB0BFWQZ@FBGA64 [DX5001]
S71PL129JC0BAI9U@FBGA64 [DX5001]
S71PL129JC0BAI9Z@FBGA64 [DX5001]
S71PL129JC0BAW9B@FBGA64 [DX5001]
S71PL129JC0BAW9U@FBGA64 [DX5001]
S71PL129JC0BAW9Z@FBGA64 [DX5001]
S71PL129JC0BFI9U@FBGA64 [DX5001]
S71PL129JC0BFI9Z@FBGA64 [DX5001]
S71PL129JC0BFW9B@FBGA64 [DX5001]
S71PL129JC0BFW9U@FBGA64 [DX5001]
S71PL129JC0BFW9Z@FBGA64 [DX5001]
S71PL129NB0HAW4B@FBGA64 [DX5001]
S71PL129NB0HAW4U@FBGA64 [DX5001]
S71PL129NB0HAW4Z@FBGA64 [DX5001]
S71PL129NB0HFW4B@FBGA64 [DX5001]
S71PL129NB0HFW4U@FBGA64 [DX5001]
S71PL129NB0HFW4Z@FBGA64 [DX5001]
S71PL129NC0HAW4B@FBGA64 [DX5001]
S71PL129NC0HAW4U@FBGA64 [DX5001]
S71PL129NC0HFW4B@FBGA64 [DX5001]
S71PL129NC0HFW4U@FBGA64 [DX5001]
S71PL191HB0BAI10@FBGA73 [DX5057]
S71PL191HB0BAW10@FBGA73 [DX5057]

S71PL191HB0BFI10@FBGA73 [DX5057]
S71PL191HB0BFW10@FBGA73 [DX5057]
S71PL191HC0BAI10@FBGA73 [DX5057]
S71PL191HC0BAW10@FBGA73 [DX5057]
S71PL191HC0BFI10@FBGA73 [DX5057]
S71PL191HC0BFW10@FBGA73 [DX5057]
S71PL193HB0BAI10@FBGA73 [DX5072]
S71PL193HB0BAW10@FBGA73 [DX5072]
S71PL193HB0BFI10@FBGA73 [DX5072]
S71PL193HB0BFW10@FBGA73 [DX5072]
S71PL193HC0BAI10@FBGA73 [DX5072]
S71PL193HC0BAW10@FBGA73 [DX5072]
S71PL193HC0BFI10@FBGA73 [DX5072]
S71PL193HC0BFW10@FBGA73 [DX5072]
S71PL254J04BAITZ@FBGA84 [DX5001]
S71PL254J04BAWTZ@FBGA84 [DX5001]
S71PL254J04BFITZ@FBGA84 [DX5001]
S71PL254J04BFWTZ@FBGA84 [DX5001]
S71PL254J08BAITZ@FBGA84 [DX5001]
S71PL254J08BAWTZ@FBGA84 [DX5001]
S71PL254J08BFITZ@FBGA84 [DX5001]
S71PL254J08BFWTZ@FBGA84 [DX5001]
S71PL254J40BAITZ@FBGA84 [DX5001]
S71PL254J40BAWTZ@FBGA84 [DX5001]
S71PL254J40BFITZ@FBGA84 [DX5001]
S71PL254J40BFWTZ@FBGA84 [DX5001]
S71PL254J80BAITZ@FBGA84 [DX5001]
S71PL254J80BAWTZ@FBGA84 [DX5001]
S71PL254J80BFWIZ@FBGA84 [DX5001]
S71PL254J80BFWTZ@FBGA84 [DX5001]
S71PL254JA0BAITZ@FBGA84 [DX5001]
S71PL254JA0BAWTZ@FBGA84 [DX5001]
S71PL254JA0BFITZ@FBGA84 [DX5001]
S71PL254JA0BFWTZ@FBGA84 [DX5001]
S71PL254JB0BAIT7@FBGA84 [DX5001]
S71PL254JB0BAITB@FBGA84 [DX5001]
S71PL254JB0BAITU@FBGA84 [DX5001]
S71PL254JB0BAITZ@FBGA84 [DX5001]
S71PL254JB0BAWT7@FBGA84 [DX5001]
S71PL254JB0BAWTB@FBGA84 [DX5001]
S71PL254JB0BAWTU@FBGA84 [DX5001]
S71PL254JB0BAWTZ@FBGA84 [DX5001]
S71PL254JB0BFIT7@FBGA84 [DX5001]
S71PL254JB0BFITB@FBGA84 [DX5001]
S71PL254JB0BFITU@FBGA84 [DX5001]
S71PL254JB0BFITZ@FBGA84 [DX5001]
S71PL254JB0BFWT7@FBGA84 [DX5001]
S71PL254JB0BFWTB@FBGA84 [DX5001]
S71PL254JB0BFWTU@FBGA84 [DX5001]
S71PL254JB0BFWTZ@FBGA84 [DX5001]
S71PL254JC0BAITB@FBGA84 [DX5001]
S71PL254JC0BAITU@FBGA84 [DX5001]
S71PL254JC0BAITZ@FBGA84 [DX5001]
S71PL254JC0BAWTB@FBGA84 [DX5001]
S71PL254JC0BAWTU@FBGA84 [DX5001]
S71PL254JC0BAWTZ@FBGA84 [DX5001]
S71PL254JC0BFITB@FBGA84 [DX5001]
S71PL254JC0BFITU@FBGA84 [DX5001]
S71PL254JC0BFITZ@FBGA84 [DX5001]
S71PL254JC0BFWTB@FBGA84 [DX5001]
S71PL254JC0BFWTU@FBGA84 [DX5001]
S71PL254JC0BFWTZ@FBGA84 [DX5001]
S71PL254JD0BAWTB@FBGA84 [DX5001]
S71PL254JD0BFWTB@FBGA84 [DX5001]
S71PL256NC0HAW5B@FBGA84 [DX5001]
S71PL256NC0HAW5U@FBGA84 [DX5001]
S71PL256NC0HFW5B@FBGA84 [DX5001]
S71PL256NC0HFW5U@FBGA84 [DX5001]
S71PL256ND0GAW5B@FBGA84 [DX5001]
S71PL256ND0GFW5B@FBGA84 [DX5001]
S71PL256ND0HAW5B@FBGA84 [DX5001]
S71PL256ND0HAW5U@FBGA84 [DX5001]
S71PL256ND0HFW5B@FBGA84 [DX5001]
S71PL256ND0HFW5U@FBGA84 [DX5001]
S71PL512ND0JAW5B@FBGA84 [DX5001]
S71PL512ND0JFW5B@FBGA84 [DX5001]
S71VS032K80ZJK01@FBGA56 [DX5094]
S71VS032K80ZJK03@FBGA56 [DX5094]
S71VS032KA0ZJK09@FBGA56 [DX5094]
S71VS032KA0ZJK0B@FBGA56 [DX5094]
S71VS032KA0ZJK11@FBGA56 [DX5094]
S71VS032KA0ZJK13@FBGA56 [DX5094]
S71VS032KA0ZJK19@FBGA56 [DX5094]
S71VS032KA0ZJK1B@FBGA56 [DX5094]
S71VS064KA0ZJK01@FBGA56 [DX5094]
S71VS064KA0ZJK03@FBGA56 [DX5094]
S71VS064KA0ZJK09@FBGA56 [DX5094]
S71VS064KA0ZJK0B@FBGA56 [DX5094]
S71VS064KA0ZJK11@FBGA56 [DX5094]
S71VS064KA0ZJK13@FBGA56 [DX5094]
S71VS064KA0ZJK19@FBGA56 [DX5094]
S71VS064KA0ZJK1B@FBGA56 [DX5094]
S71VS064RB0AHT0L@FBGA52 [DX5199]
S71VS064RB0AHT0M@FBGA52 [DX5199]
S71VS064RB0AHT3L@FBGA52 [DX5199]
S71VS064RB0AHT4L@FBGA52 [DX5199]

S71VS064RB0AHT8L@FBGA52 [DX5199]　　S71VS064RB0AHT8M@FBGA52 [DX5199]
S71VS064RB0AHTBL@FBGA52 [DX5199]　　S71VS064RB0AHTCL@FBGA52 [DX5199]
S71VS128RB0AHK0L@FBGA56 [DX5094]　　S71VS128RB0AHK2L@FBGA56 [DX5094]
S71VS128RB0AHK3L@FBGA56 [DX5094]　　S71VS128RB0AHK4L@FBGA56 [DX5094]
S71VS128RB0AHK4L@FBGA56(test) [DX5094]
S71VS128RB0AHK4S@FBGA56 [DX5094]　　S71VS128RB0AHK8L@FBGA56 [DX5094]
S71VS128RB0AHKAL@FBGA56 [DX5094]　　S71VS128RC0AHK20@FBGA56 [DX5094]
S71VS128RC0AHK3L@FBGA56(wdk) [DX5094]
S71VS128RC0AHK4L@FBGA56 [DX5094]
S71VS128RC0AHK4L@FBGA56(spec) [DX5094]
S71VS128RC0AHK4L@FBGA56(wdk) [DX5094]
S71VS128RC0AHKCL@FBGA56 [DX5094]　　S71VS128RC0ZHK20@FBGA56 [DX5094]
S71VS128RC0ZHK24@FBGA56 [DX5094]　　S71VS128RC0ZHKA0@FBGA56 [DX5094]
S71VS128RC0ZHKA4@FBGA56 [DX5094]　　S71VS256RC0AHK4L@FBGA56 [DX5094]
S71VS256RC0AHKCL@FBGA56 [DX5094]　　S71VS256RC0ZHK20@FBGA56 [DX5094]
S71VS256RC0ZHK24@FBGA56 [DX5094]　　S71VS256RC0ZHKA0@FBGA56 [DX5094]
S71VS256RC0ZHKA4@FBGA56 [DX5094]　　S71VS256RD0AHK3C@FBGA56 [DX5094]
S71VS256RD0AHK3L@FBGA56 [DX5094]　　S71VS256RD0AHKBC@FBGA56 [DX5094]
S71VS256RD0AHKBL@FBGA56 [DX5094]　　S71VS256RD0ZHE40@FBGA56 [DX5066]
S71VS256RD0ZHE44@FBGA56 [DX5066]
S71VS256RD0ZHEC0(BN)@FBGA56 [DX5066]
S71VS256RD0ZHEC0@FBGA56 [DX5066]　　S71VS256RD0ZHEC4@FBGA56 [DX5066]
S71WS064JA0BAI2A@FBGA80 [DX5052]　　S71WS064JA0BAI2Y@FBGA80 [DX5052]
S71WS064JA0BAW2A@FBGA80 [DX5052]　　S71WS064JA0BAW2Y@FBGA80 [DX5052]
S71WS064JA0BFI2A@FBGA80 [DX5052]　　S71WS064JA0BFI2Y@FBGA80 [DX5052]
S71WS064JA0BFW2A@FBGA80 [DX5052]　　S71WS064JA0BFW2Y@FBGA80 [DX5052]
S71WS064JB0BAI2A@FBGA80 [DX5052]　　S71WS064JB0BAI2Y@FBGA80 [DX5052]
S71WS064JB0BAW2A@FBGA80 [DX5052]　　S71WS064JB0BAW2Y@FBGA80 [DX5052]
S71WS064JB0BFI2A@FBGA80 [DX5052]　　S71WS064JB0BFI2Y@FBGA80 [DX5052]
S71WS064JB0BFW2A@FBGA80 [DX5052]　　S71WS064JB0BFW2Y@FBGA80 [DX5052]
S71WS128HC0BAWA7@FBGA88 [DX5001]　　S71WS128HC0BAWAB@FBGA88 [DX5001]
S71WS128HC0BFWA7@FBGA88 [DX5001]　　S71WS128HC0BFWAB@FBGA88 [DX5001]
S71WS128JA0BAIAA@FBGA84 [DX5001]　　S71WS128JA0BAIAJ@FBGA84 [DX5001]
S71WS128JA0BAWAA@FBGA84 [DX5001]　　S71WS128JA0BAWAJ@FBGA84 [DX5001]
S71WS128JA0BFIAA@FBGA84 [DX5001]　　S71WS128JA0BFIAJ@FBGA84 [DX5001]
S71WS128JA0BFWAA@FBGA84 [DX5001]　　S71WS128JA0BFWAJ@FBGA84 [DX5001]
S71WS128JB0BAE9Y@FBGA84 [DX5001]　　S71WS128JB0BAIAA@FBGA84 [DX5001]
S71WS128JB0BAIAJ@FBGA84 [DX5001]　　S71WS128JB0BAIAY@FBGA84 [DX5001]
S71WS128JB0BAWAA@FBGA84 [DX5001]　　S71WS128JB0BAWAJ@FBGA84 [DX5001]
S71WS128JB0BAWAY@FBGA84 [DX5001]　　S71WS128JB0BFIAA@FBGA84 [DX5001]
S71WS128JB0BFIAJ@FBGA84 [DX5001]　　S71WS128JB0BFIAY@FBGA84 [DX5001]
S71WS128JB0BFWAA@FBGA84 [DX5001]　　S71WS128JB0BFWAJ@FBGA84 [DX5001]
S71WS128JB0BFWAY@FBGA84 [DX5001]　　S71WS128JC0BAE9A@FBGA84 [DX5001]
S71WS128JC0BAE9Y@FBGA84 [DX5001]　　S71WS128JC0BAIA6@FBGA84 [DX5001]
S71WS128JC0BAIAA@FBGA84 [DX5001]　　S71WS128JC0BAIAJ@FBGA84 [DX5001]
S71WS128JC0BAIAY@FBGA84 [DX5001]　　S71WS128JC0BAWA6@FBGA84 [DX5001]
S71WS128JC0BAWAA@FBGA84 [DX5001]　　S71WS128JC0BAWAJ@FBGA84 [DX5001]
S71WS128JC0BAWAY@FBGA84 [DX5001]　　S71WS128JC0BFE9A@FBGA84 [DX5001]

S71WS128JC0BFIA6@FBGA84 [DX5001]
S71WS128JC0BFIAA@FBGA84 [DX5001]
S71WS128JC0BFIAJ@FBGA84 [DX5001]
S71WS128JC0BFIAY@FBGA84 [DX5001]
S71WS128JC0BFW9Y@FBGA84 [DX5001]
S71WS128JC0BFWA6@FBGA84 [DX5001]
S71WS128JC0BFWAA@FBGA84 [DX5001]
S71WS128JC0BFWAJ@FBGA84 [DX5001]
S71WS128JC0BFWAY@FBGA84 [DX5001]
S71WS128NB0BAWAH@FBGA84 [DX5001]
S71WS128NB0BAWAJ@FBGA84 [DX5001]
S71WS128NB0BAWAK@FBGA84 [DX5001]
S71WS128NB0BAWAM@FBGA84 [DX5001]
S71WS128NB0BAWAN@FBGA84 [DX5001]
S71WS128NB0BAWAP@FBGA84 [DX5001]
S71WS128NB0BFWAH@FBGA84 [DX5001]
S71WS128NB0BFWAJ@FBGA84 [DX5001]
S71WS128NB0BFWAK@FBGA84 [DX5001]
S71WS128NB0BFWAM@FBGA84 [DX5001]
S71WS128NB0BFWAN@FBGA84 [DX5001]
S71WS128NB0BFWAP@FBGA84 [DX5001]
S71WS128NC0BAWA2@FBGA84 [DX5001]
S71WS128NC0BAWA3@FBGA84 [DX5001]
S71WS128NC0BAWA6@FBGA84 [DX5001]
S71WS128NC0BAWA7@FBGA84 [DX5001]
S71WS128NC0BAWAH@FBGA84 [DX5001]
S71WS128NC0BAWAJ@FBGA84 [DX5001]
S71WS128NC0BAWAK@FBGA84 [DX5001]
S71WS128NC0BAWAM@FBGA84 [DX5001]
S71WS128NC0BAWAN@FBGA84 [DX5001]
S71WS128NC0BAWAP@FBGA84 [DX5001]
S71WS128NC0BFWA2@FBGA84 [DX5001]
S71WS128NC0BFWA3@FBGA84 [DX5001]
S71WS128NC0BFWA6@FBGA84 [DX5001]
S71WS128NC0BFWA7@FBGA84 [DX5001]
S71WS128NC0BFWAH@FBGA84 [DX5001]
S71WS128NC0BFWAJ@FBGA84 [DX5001]
S71WS128NC0BFWAK@FBGA84 [DX5001]
S71WS128NC0BFWAM@FBGA84 [DX5001]
S71WS128NC0BFWAN@FBGA84 [DX5001]
S71WS128NC0BFWAP@FBGA84 [DX5001]
S71WS128PB0HF3SL@FBGA84 [DX5001]
S71WS128PB0HF3SR@FBGA84 [DX5001]
S71WS128PB0HF3SV@FBGA84 [DX5001]
S71WS128PB0HH3RR@FBGA84 [DX5001]
S71WS128PB0HH3SL@FBGA84 [DX5001]
S71WS128PB0HH3SR@FBGA84 [DX5001]
S71WS128PB0HH3SV@FBGA84 [DX5001]
S71WS128PC0HF3SL@FBGA84 [DX5001]
S71WS128PC0HF3SR@FBGA84 [DX5001]
S71WS128PC0HF3SV@FBGA84 [DX5001]
S71WS128PC0HF3SZ@FBGA84 [DX5180]
S71WS128PC0HF3TR@FBGA84 [DX5001]
S71WS128PC0HH3SL@FBGA84 [DX5001]
S71WS128PC0HH3SR@FBGA84 [DX5001]
S71WS128PC0HH3SV@FBGA84 [DX5001]
S71WS128RB0HH309@FBGA84 [DX5001]
S71WS128RB0HH30A@FBGA84 [DX5001]
S71WS128RB0HH329@FBGA84 [DX5001]
S71WS128RB0HH32A@FBGA84 [DX5001]
S71WS128RC0HH309@FBGA84 [DX5001]
S71WS128RC0HH30A@FBGA84 [DX5001]
S71WS128RC0HH329@FBGA84 [DX5001]
S71WS128RC0HH32A@FBGA84 [DX5001]
S71WS256JC0BAIA6@FBGA84 [DX5001]
S71WS256JC0BAIAJ@FBGA84 [DX5001]
S71WS256JC0BAIAY@FBGA84 [DX5001]
S71WS256JC0BAIT6@FBGA84 [DX5001]
S71WS256JC0BAITJ@FBGA84 [DX5001]
S71WS256JC0BAITY@FBGA84 [DX5001]
S71WS256JC0BAWA6@FBGA84 [DX5001]
S71WS256JC0BAWAJ@FBGA84 [DX5001]
S71WS256JC0BAWAY@FBGA84 [DX5001]
S71WS256JC0BAWT6@FBGA84 [DX5001]
S71WS256JC0BAWTJ@FBGA84 [DX5001]
S71WS256JC0BAWTY@FBGA84 [DX5001]
S71WS256JC0BFIA6@FBGA84 [DX5001]
S71WS256JC0BFIAJ@FBGA84 [DX5001]
S71WS256JC0BFIAY@FBGA84 [DX5001]
S71WS256JC0BFIT6@FBGA84 [DX5001]
S71WS256JC0BFITJ@FBGA84 [DX5001]
S71WS256JC0BFITY@FBGA84 [DX5001]
S71WS256JC0BFWA6@FBGA84 [DX5001]
S71WS256JC0BFWAJ@FBGA84 [DX5001]
S71WS256JC0BFWAY@FBGA84 [DX5001]
S71WS256JC0BFWT6@FBGA84 [DX5001]
S71WS256JC0BFWTJ@FBGA84 [DX5001]
S71WS256JC0BFWTY@FBGA84 [DX5001]
S71WS256NC0BAIAB@FBGA84 [DX5001]
S71WS256NC0BAIAF@FBGA84 [DX5001]
S71WS256NC0BAIAK@FBGA84 [DX5001]
S71WS256NC0BAIAP@FBGA84 [DX5001]
S71WS256NC0BAIAU@FBGA84 [DX5001]
S71WS256NC0BAIAZ@FBGA84 [DX5001]
S71WS256NC0BAWA2@FBGA84 [DX5001]
S71WS256NC0BAWA3@FBGA84 [DX5001]

S71WS256NC0BAWA6@FBGA84 [DX5001]
S71WS256NC0BAWA7@FBGA84 [DX5001]
S71WS256NC0BAWAA@FBGA84 [DX5001]
S71WS256NC0BAWAB@FBGA84 [DX5001]
S71WS256NC0BAWAE@FBGA84 [DX5001]
S71WS256NC0BAWAF@FBGA84 [DX5001]
S71WS256NC0BAWAH@FBGA84 [DX5001]
S71WS256NC0BAWAJ@FBGA84 [DX5001]
S71WS256NC0BAWAK@FBGA84 [DX5001]
S71WS256NC0BAWAM@FBGA84 [DX5001]
S71WS256NC0BAWAN@FBGA84 [DX5001]
S71WS256NC0BAWAP@FBGA84 [DX5001]
S71WS256NC0BAWAU@FBGA84 [DX5001]
S71WS256NC0BAWAZ@FBGA84 [DX5001]
S71WS256NC0BFIAB@FBGA84 [DX5001]
S71WS256NC0BFIAF@FBGA84 [DX5001]
S71WS256NC0BFIAK@FBGA84 [DX5001]
S71WS256NC0BFIAP@FBGA84 [DX5001]
S71WS256NC0BFIAU@FBGA84 [DX5001]
S71WS256NC0BFIAZ@FBGA84 [DX5001]
S71WS256NC0BFWA2@FBGA84 [DX5001]
S71WS256NC0BFWA3@FBGA84 [DX5001]
S71WS256NC0BFWA6@FBGA84 [DX5001]
S71WS256NC0BFWA7@FBGA84 [DX5001]
S71WS256NC0BFWAA@FBGA84 [DX5001]
S71WS256NC0BFWAB@FBGA84 [DX5001]
S71WS256NC0BFWAE@FBGA84 [DX5001]
S71WS256NC0BFWAF@FBGA84 [DX5001]
S71WS256NC0BFWAH@FBGA84 [DX5001]
S71WS256NC0BFWAJ@FBGA84 [DX5001]
S71WS256NC0BFWAK@FBGA84 [DX5001]
S71WS256NC0BFWAM@FBGA84 [DX5001]
S71WS256NC0BFWAN@FBGA84 [DX5001]
S71WS256NC0BFWAP@FBGA84 [DX5001]
S71WS256NC0BFWAU@FBGA84 [DX5001]
S71WS256NC0BFWAZ@FBGA84 [DX5001]
S71WS256ND0BAIE3@FBGA84 [DX5054]
S71WS256ND0BAIE7@FBGA84 [DX5054]
S71WS256ND0BAIEK@FBGA84 [DX5054]
S71WS256ND0BAIEP@FBGA84 [DX5054]
S71WS256ND0BAIEU@FBGA84 [DX5054]
S71WS256ND0BAIEZ@FBGA84 [DX5054]
S71WS256ND0BAWE3@FBGA84 [DX5054]
S71WS256ND0BAWE7@FBGA84 [DX5054]
S71WS256ND0BAWEK@FBGA84 [DX5054]
S71WS256ND0BAWEP@FBGA84 [DX5054]
S71WS256ND0BAWEU@FBGA84 [DX5054]
S71WS256ND0BAWEZ@FBGA84 [DX5054]
S71WS256ND0BAWYH@FBGA84 [DX5054]
S71WS256ND0BAWYJ@FBGA84 [DX5054]
S71WS256ND0BAWYK@FBGA84 [DX5054]
S71WS256ND0BAWYM@FBGA84 [DX5054]
S71WS256ND0BAWYN@FBGA84 [DX5054]
S71WS256ND0BAWYP@FBGA84 [DX5054]
S71WS256ND0BFIE3@FBGA84 [DX5054]
S71WS256ND0BFIE7@FBGA84 [DX5054]
S71WS256ND0BFIEK@FBGA84 [DX5054]
S71WS256ND0BFIEP@FBGA84 [DX5054]
S71WS256ND0BFIEU@FBGA84 [DX5054]
S71WS256ND0BFIEZ@FBGA84 [DX5054]
S71WS256ND0BFWE3@FBGA84 [DX5054]
S71WS256ND0BFWE7@FBGA84 [DX5054]
S71WS256ND0BFWEK@FBGA84 [DX5054]
S71WS256ND0BFWEP@FBGA84 [DX5054]
S71WS256ND0BFWEU@FBGA84 [DX5054]
S71WS256ND0BFWEZ@FBGA84 [DX5054]
S71WS256ND0BFWYH@FBGA84 [DX5054]
S71WS256ND0BFWYJ@FBGA84 [DX5054]
S71WS256ND0BFWYK@FBGA84 [DX5054]
S71WS256ND0BFWYM@FBGA84 [DX5054]
S71WS256ND0BFWYN@FBGA84 [DX5054]
S71WS256ND0BFWYP@FBGA84 [DX5054]
S71WS256PC0HF3SL@FBGA84 [DX5001]
S71WS256PC0HF3SR@FBGA84 [DX5001]
S71WS256PC0HF3SV@FBGA84 [DX5001]
S71WS256PC0HH3SL@FBGA84 [DX5001]
S71WS256PC0HH3SR@FBGA84 [DX5001]
S71WS256PC0HH3SV@FBGA84 [DX5001]
S71WS256PC0HH3YL@FBGA84 [DX5001]
S71WS256PC0HH3YR@FBGA84 [DX5001]
S71WS256PD0HF3SL@FBGA84 [DX5001]
S71WS256PD0HF3SR@FBGA84 [DX5001]
S71WS256PD0HF3SV@FBGA84 [DX5001]
S71WS256PD0HF3SZ@FBGA84 [DX5180]
S71WS256PD0HF3TL@FBGA84 [DX5001]
S71WS256PD0HF3TR@FBGA84 [DX5001]
S71WS256PD0HH3SL@FBGA84 [DX5001]
S71WS256PD0HH3SR@FBGA84 [DX5001]
S71WS256PD0HH3SV@FBGA84 [DX5001]
S71WS256PD0HH3YL@FBGA84 [DX5001]
S71WS256PD0HH3YR@FBGA84 [DX5001]
S71WS256PD0HH3YV@FBGA84 [DX5001]
S71WS256PD0HH3YZ@FBGA84 [DX5180]
S71WS256RC0HH309@FBGA84 [DX5001]
S71WS256RC0HH30A@FBGA84 [DX5001]
S71WS256RC0HH329@FBGA84 [DX5001]

S71WS256RC0HH32A@FBGA84 [DX5001]
S71WS256RD0HH309@FBGA84 [DX5001]
S71WS256RD0HH30A@FBGA84 [DX5001]
S71WS256RD0HH329@FBGA84 [DX5001]
S71WS256RD0HH32A@FBGA84 [DX5001]
S71WS512NC0BAIAB@FBGA84 [DX5001]
S71WS512NC0BAIAF@FBGA84 [DX5001]
S71WS512NC0BAIAK@FBGA84 [DX5001]
S71WS512NC0BAIAP@FBGA84 [DX5001]
S71WS512NC0BAIAU@FBGA84 [DX5001]
S71WS512NC0BAIAZ@FBGA84 [DX5001]
S71WS512NC0BAWAB@FBGA84 [DX5001]
S71WS512NC0BAWAF@FBGA84 [DX5001]
S71WS512NC0BAWAK@FBGA84 [DX5001]
S71WS512NC0BAWAP@FBGA84 [DX5001]
S71WS512NC0BAWAU@FBGA84 [DX5001]
S71WS512NC0BAWAZ@FBGA84 [DX5001]
S71WS512NC0BAWTA@FBGA84 [DX5001]
S71WS512NC0BAWTE@FBGA84 [DX5001]
S71WS512NC0BAWTH@FBGA84 [DX5001]
S71WS512NC0BAWTJ@FBGA84 [DX5001]
S71WS512NC0BAWTM@FBGA84 [DX5001]
S71WS512NC0BAWTN@FBGA84 [DX5001]
S71WS512NC0BFIAB@FBGA84 [DX5001]
S71WS512NC0BFIAF@FBGA84 [DX5001]
S71WS512NC0BFIAK@FBGA84 [DX5001]
S71WS512NC0BFIAP@FBGA84 [DX5001]
S71WS512NC0BFIAU@FBGA84 [DX5001]
S71WS512NC0BFIAZ@FBGA84 [DX5001]
S71WS512NC0BFWAB@FBGA84 [DX5001]
S71WS512NC0BFWAF@FBGA84 [DX5001]
S71WS512NC0BFWAK@FBGA84 [DX5001]
S71WS512NC0BFWAP@FBGA84 [DX5001]
S71WS512NC0BFWAU@FBGA84 [DX5001]
S71WS512NC0BFWAZ@FBGA84 [DX5001]
S71WS512NC0BFWTA@FBGA84 [DX5001]
S71WS512NC0BFWTE@FBGA84 [DX5001]
S71WS512NC0BFWTH@FBGA84 [DX5001]
S71WS512NC0BFWTJ@FBGA84 [DX5001]
S71WS512NC0BFWTM@FBGA84 [DX5001]
S71WS512NC0BFWTN@FBGA84 [DX5001]
S71WS512ND0BAIE3@FBGA84 [DX5054]
S71WS512ND0BAIE7@FBGA84 [DX5054]
S71WS512ND0BAIEK@FBGA84 [DX5054]
S71WS512ND0BAIEP@FBGA84 [DX5054]
S71WS512ND0BAWE2@FBGA84 [DX5054]
S71WS512ND0BAWE3@FBGA84 [DX5054]
S71WS512ND0BAWE6@FBGA84 [DX5054]
S71WS512ND0BAWE7@FBGA84 [DX5054]
S71WS512ND0BAWEH@FBGA84 [DX5054]
S71WS512ND0BAWEJ@FBGA84 [DX5054]
S71WS512ND0BAWEK@FBGA84 [DX5054]
S71WS512ND0BAWEM@FBGA84 [DX5054]
S71WS512ND0BAWEN@FBGA84 [DX5054]
S71WS512ND0BAWEP@FBGA84 [DX5054]
S71WS512ND0BFIE3@FBGA84 [DX5054]
S71WS512ND0BFIE7@FBGA84 [DX5054]
S71WS512ND0BFIEK@FBGA84 [DX5054]
S71WS512ND0BFIEP@FBGA84 [DX5054]
S71WS512ND0BFWE2@FBGA84 [DX5054]
S71WS512ND0BFWE3@FBGA84 [DX5054]
S71WS512ND0BFWE6@FBGA84 [DX5054]
S71WS512ND0BFWE7@FBGA84 [DX5054]
S71WS512ND0BFWEH@FBGA84 [DX5054]
S71WS512ND0BFWEJ@FBGA84 [DX5054]
S71WS512ND0BFWEK@FBGA84 [DX5054]
S71WS512ND0BFWEM@FBGA84 [DX5054]
S71WS512ND0BFWEN@FBGA84 [DX5054]
S71WS512ND0BFWEP@FBGA84 [DX5054]
S71WS512PC0HF3S2@FBGA84 [DX5001]
S71WS512PC0HF3SL@FBGA84 [DX5001]
S71WS512PC0HF3SR@FBGA84 [DX5001]
S71WS512PC0HF3SV@FBGA84 [DX5001]
S71WS512PC0HF3SW@FBGA84 [DX5001]
S71WS512PD0HF3HR@FBGA84 [DX5001]
S71WS512PD0HF3SL@FBGA84 [DX5001]
S71WS512PD0HF3SR@FBGA84 [DX5001]
S71WS512PD0HF3TL@FBGA84 [DX5001]
S71WS512PD0HF3TR@FBGA84 [DX5001]
S71WS512PD0HH3SL@FBGA84 [DX5001]
S71WS512PD0HH3SR@FBGA84 [DX5001]
S71WS512PD0HH3YL@FBGA84 [DX5001]
S71WS512PD0HH3YR@FBGA84 [DX5001]
S71WS512PD0HH3YV@FBGA84 [DX5001]
S71WS512RD0HH309@FBGA84 [DX5001]
S71WS512RD0HH30A@FBGA84 [DX5001]
S71WS512RD0HH329@FBGA84 [DX5001]
S71WS512RD0HH32A@FBGA84 [DX5001]
S72NS128ND0AFW12@FBGA133 [DX5069]
S72NS128ND0AFW13@FBGA133 [DX5069]
S72NS128ND0AFW1J@FBGA133 [DX5069]
S72NS128ND0AFW1K@FBGA133 [DX5069]

S72NS128ND0AJW12@FBGA133 [DX5069]
S72NS128ND0AJW13@FBGA133 [DX5069]
S72NS128ND0AJW1J@FBGA133 [DX5069]
S72NS128ND0AJW1K@FBGA133 [DX5069]
S72NS128PD0AHBLC@FBGA133 [DX5069]
S72NS128PD0AHBLG@FBGA133 [DX5069]
S72NS128PD0AJBGC@FBGA133 [DX5069]
S72NS128PD0AJBGG@FBGA133 [DX5069]
S72NS128RD0AHBG0@FBGA133 [DX5069]
S72NS128RD0AHBL0@FBGA133 [DX5069]
S72NS128RD0AHBM0@FBGA133 [DX5069]
S72NS256ND0AFW72@FBGA133 [DX5098]
S72NS256ND0AFW73@FBGA133 [DX5098]
S72NS256ND0AFW7J@FBGA133 [DX5098]
S72NS256ND0AFW7K@FBGA133 [DX5098]
S72NS256ND0AJW72@FBGA133 [DX5098]
S72NS256ND0AJW73@FBGA133 [DX5098]
S72NS256ND0AJW7J@FBGA133 [DX5098]
S72NS256ND0AJW7K@FBGA133 [DX5098]
S72NS256PD0AJBGC@FBGA133 [DX5069]
S72NS256PD0AJBGG@FBGA133 [DX5069]
S72NS256PD0AJBLC@FBGA133 [DX5069]
S72NS256PD0AJBLG@FBGA133 [DX5069]
S72NS256RD0AHBG0@FBGA133 [DX5069]
S72NS256RD0AHBL0@FBGA133 [DX5069]
S72NS256RD0AHBM0@FBGA133 [DX5069]
S72NS512ND0ZJW72@FBGA133 [DX5098]
S72NS512ND0ZJW73@FBGA133 [DX5098]
S72NS512ND0ZJW7J@FBGA133 [DX5098]
S72NS512ND0ZJW7K@FBGA133 [DX5098]
S72NS512NE0ZJW72@FBGA133 [DX5098]
S72NS512NE0ZJW73@FBGA133 [DX5098]
S72NS512NE0ZJW7J@FBGA133 [DX5098]
S72NS512NE0ZJW7K@FBGA133 [DX5098]
S72NS512PD0AHGLG@FBGA133 [DX5098]
S72NS512PD0AJGGC@FBGA133 [DX5098]
S72NS512PD0AJGGG@FBGA133 [DX5098]
S72NS512PD0AJGLC@FBGA133 [DX5098]
S72NS512PD0AJGLG@FBGA133 [DX5098]
S72NS512PE0AJGLC@FBGA133 [DX5098]
S72NS512PE0AJGLG@FBGA133 [DX5098]
S72NS512RD0AHGG0@FBGA133 [DX5098]
S72NS512RD0AHGL0@FBGA133 [DX5098]
S72NS512RD0AHGM0@FBGA133 [DX5098]
S72NS512RE0AHGG0@FBGA133 [DX5098]
S72NS512RE0AHGL0@FBGA133 [DX5098]
S72WS256ND0KFWD3@FBGA160 [DX5105]
S72WS512NEFKFWHJ@FBGA160 [DX5105]

S72WS512NEFKFWZ2@FBGA160 [DX5105]
S72WS512NEFKFWZJ@FBGA160 [DX5105]
S72WS512NEFKFWZT@FBGA160 [DX5105]
S72WS512NEG-4W@FBGA137 [DX5086]
S72WS512NEG-4Y@FBGA137 [DX5086]
S72WS512NEG-4Z@FBGA137 [DX5086]
S72WS512NEG-6W@FBGA137 [DX5086]
S72WS512NEG-6Y@FBGA137 [DX5086]
S72WS512NEG-6Z@FBGA137 [DX5086]
S72WS512NEG-LW@FBGA137 [DX5086]
S72WS512NEG-LY@FBGA137 [DX5086]
S72WS512NEG-LZ@FBGA137 [DX5086]
S72WS512NEG-NW@FBGA137 [DX5086]
S72WS512NEG-NY@FBGA137 [DX5086]
S72WS512NEG-NZ@FBGA137 [DX5086]
S72WS512NFFBFWZ2@FBGA137 [DX5086]
S72WS512NFFBFWZJ@FBGA137 [DX5086]
S72WS512NFG-45@FBGA137 [DX5086]
S72WS512NFG-46@FBGA137 [DX5086]
S72WS512NFG-47@FBGA137 [DX5086]
S72WS512NFG-4W@FBGA137 [DX5086]
S72WS512NFG-4Y@FBGA137 [DX5086]
S72WS512NFG-4Z@FBGA137 [DX5086]
S72WS512NFG-65@FBGA137 [DX5086]
S72WS512NFG-66@FBGA137 [DX5086]
S72WS512NFG-67@FBGA137 [DX5086]
S72WS512NFG-6W@FBGA137 [DX5086]
S72WS512NFG-6Y@FBGA137 [DX5086]
S72WS512NFG-6Z@FBGA137 [DX5086]
S72WS512NFG-L5@FBGA137 [DX5086]
S72WS512NFG-L6@FBGA137 [DX5086]
S72WS512NFG-L7@FBGA137 [DX5086]
S72WS512NFG-LW@FBGA137 [DX5086]
S72WS512NFG-LY@FBGA137 [DX5086]
S72WS512NFG-LZ@FBGA137 [DX5086]
S72WS512NFG-N5@FBGA137 [DX5086]
S72WS512NFG-N6@FBGA137 [DX5086]
S72WS512NFG-N7@FBGA137 [DX5086]
S72WS512NFG-NW@FBGA137 [DX5086]
S72WS512NFG-NY@FBGA137 [DX5086]
S72WS512NFG-NZ@FBGA137 [DX5086]
S72WS512PEFKFKHJ@FBGA160 [DX5105]
S72WS512PFFJF9GJ@FBGA137 [DX5086]
S72WS512PFFJF9LD@FBGA137 [DX5086]
S72WS512PFFKFKGH@FBGA160 [DX5105]
S72WS512PFFKFKGJ@FBGA160 [DX5105]
S72WS512PFFKFKLD@FBGA160 [DX5105]
S72WS512PFFKFKLE@FBGA160 [DX5105]
S72WS512PFFKFKLF@FBGA160 [DX5105]
S72WS512PFGKFKGH@FBGA160 [DX5105]
S72WS512RE0HH6GN@FBGA137 [DX5129]
S73WS256NDFBFW@FBGA103 [DX5056]
S73WS512PD0HF64V@FBGA137 [DX5084]
S75PL127JBDBAWKB@FBGA84 [DX5054]
S75PL127JBDBAWKU@FBGA84 [DX5054]
S75PL127JBDBFWKB@FBGA84 [DX5054]
S75PL127JBDBFWKU@FBGA84 [DX5054]
S75PL127JBEBAWKB@FBGA84 [DX5054]
S75PL127JBEBAWKU@FBGA84 [DX5054]
S75PL127JBEBFWKB@FBGA84 [DX5054]
S75PL127JBEBFWKU@FBGA84 [DX5054]
S75PL127JBFBAWKB@FBGA84 [DX5054]
S75PL127JBFBAWKU@FBGA84 [DX5054]
S75PL127JBFBFWKB@FBGA84 [DX5054]
S75PL127JBFBFWKU@FBGA84 [DX5054]
S75PL127JCDBAWKB@FBGA84 [DX5054]
S75PL127JCDBAWKU@FBGA84 [DX5054]
S75PL127JCDBFWKB@FBGA84 [DX5054]
S75PL127JCDBFWKU@FBGA84 [DX5054]
S75PL127JCEBAWKB@FBGA84 [DX5054]
S75PL127JCEBAWKU@FBGA84 [DX5054]
S75PL127JCEBFWKB@FBGA84 [DX5054]
S75PL127JCEBFWKU@FBGA84 [DX5054]
S75PL127JCFBAWKB@FBGA84 [DX5054]
S75PL127JCFBAWKU@FBGA84 [DX5054]
S75PL127JCFBFWKB@FBGA84 [DX5054]
S75PL127JCFBFWKU@FBGA84 [DX5054]
S75WS256HCEBAWT6@FBGA115 [DX5057]

S75WS256HCEBAWT7@FBGA115 [DX5057]
S75WS256HCEBAWTA@FBGA115 [DX5057]
S75WS256HCEBAWTB@FBGA115 [DX5057]
S75WS256HCEBEW00@FBGA115 [DX5057]
S98GL064NB0HI001@FBGA56 [DX5045]　　S98GL064NB0HI002@FBGA56 [DX5045]
S98GL128PB0HW020@FBGA64 [DX5079]　　S98GL128PB0HW021@FBGA64 [DX5079]
S98NS032JA0FW001@FBGA88 [DX5001]　　S98NS128NB0FW001@FBGA88 [DX5001]
S98NS256PB0HW001@FBGA56 [DX5066]　　S98NS256RB0HW001@FBGA56 [DX5094]
S98PL191JD0AQ001@FBGA115 [DX5057]
S98PL191JD0FQ001@FBGA115 [DX5057]
S98PL191JDFAQ001(Nor)@FBGA115 [DX5057]
S98PL191JDFFQ001(Nor)@FBGA115 [DX5057]
S98WS01GPE0HW020@FBGA88 [DX5001]　　S98WS01GPE0HW022@FBGA88 [DX5001]
S98WS01GPE0HW023@FBGA88 [DX5001]
S98WS01GPGGFW001@FBGA137 [DX5086]
S98WS01GPGGFW002@FBGA137 [DX5086]
S98WS01GPGGFW003@FBGA137 [DX5086]
S98WS128NB0FW001@FBGA88 [DX5001]
S98WS128PC0FW001@FBGA107 [DX5077]
S98WS128PC0HW002@FBGA107 [DX5077]
S98WS256NEFFW001(Nor)@FBGA115 [DX5072]
S98WS256PC0FW001@FBGA88 [DX5001]
S98WS512N0GFW002(Nor)@FBGA115 [DX5072]
S98WS512N0GFW003(Nor)@FBGA115 [DX5072]
S98WS512NFFFW003@FBGA137 [DX5086]
S98WS512NFFFW005@FBGA137 [DX5086]
S98WS512NFFFW008@FBGA160 [DX5105]
S98WS512PD0FW002@FBGA107 [DX5077]
S98WS512PD0FW004@FBGA88 [DX5001]　　S98WS512PD0FW006@FBGA88 [DX5001]
S98WS512PE0FW001@FBGA103 [DX5056]
S98WS512PE0FW002@FBGA88 [DX5001]
S98WS512PE0FW006@FBGA137 [DX5084]
S98WS512PE0FW010@FBGA88 [DX5001]　　S98WS512PE0FW013@FBGA88 [DX5001]
S98WS512PE0FW014@FBGA103 [DX5056]
S98WS512PFFFW002@FBGA137 [DX5086]
S98WS512PFFFW006@FBGA137 [DX5086]
S98WS512PFFFW007@FBGA160 [DX5105]
S98WS512PFFFW011@FBGA160 [DX5105]
S98WS768P0GFW005@FBGA115 [DX5072]
S98WS768P0GFW006@FBGA115 [DX5072]
S99-50001(S29WS256N)@FBGA88 [DX5001]
S99-50003(S29WS256N)@FBGA88 [DX5001]
S99-50005(2*S29WS128H)@FBGA88 [DX5001]
S99-50011(2*S29WS256N)@FBGA103 [DX5056]
S99-50019(S29GL128N)@FBGA88 [DX5053]
S99-50031(AM29BDS320)@FBGA56 [DX5032]
S99-50034-9N(S29GL128N)@FBGA64 [DX5001]
S99-50034-9P(S29GL128N)@FBGA64 [DX5001]

S99-50034-9Y(S29GL128N)@FBGA64 [DX5001]
S99-50034-9Z(S29GL128N)@FBGA64 [DX5001]
S99-50048(S29GL064N)@FBGA64 [DX5004]
S99-50052(S29GL128N)@FBGA64 [DX5004]
S99-50057(S29GL032A)@FBGA88 [DX5053]
S99-50059(S29GL064A)@FBGA88 [DX5053]
S99-50066(S29GL032M)@FBGA88 [DX5053]
S99-50070(S29GL512N)@TSOP56 [DX1011]
S99-50073(S29WS256N)@FBGA88 [DX5001]
S99-50074(2*S29WS128J)@FBGA88 [DX5001]
S99-50076(S29WS256N)@FBGA103 [DX5056]
S99-50080(S71PL064JB0)@FBGA56 [DX5045]
S99-50080-LF(S71PL064JB0)@FBGA56 [DX5045]
S99-50085(S29WS256N)@FBGA88 [DX5001]
S99-50087(S29WS128J)@FBGA88 [DX5001]
S99-50089(2*S29WS128J)@FBGA88 [DX5001]
S99-50109(2*S29WS256N)@FBGA88 [DX5001]
S99-50111(S29AL016DFFI02)@FBGA64 [DX5074]
S99-50119@FBGA103 [DX5056]
S99-50121-9Y(S29GL128N)@FBGA64 [DX5001]
S99-50121-9Y-LF(S29GL128N)@BGA64 [DX5001]
S99-50121-9Z(S29GL128N)@FBGA64 [DX5001]
S99-50121-9Z-LF(S29GL128N)@BGA64 [DX5001]
S99-50134(S29GL128N)@FBGA88 [DX5005]
S99-50149-0(Nor)@FBGA107 [DX5084]
S99-50149-2(Nor)@FBGA107 [DX5084]
S99-50149-3(Nor)@FBGA107 [DX5084]
S99-50158(S29PL032J)@FBGA67 [DX5001]
S99-50158-LF(S29PL032J)@FBGA67 [DX5001]
S99-50183(S29GL256N)@FBGA64 [DX5004]
S99-50196(S29GL128P)@FBGA64 [DX5074]
S99-50197@FBGA64 [DX5074]
S99-50204(S29GL512P)@FBGA64 [DX5074]
S99-50206(S29GL512PFFIS1)@FBGA64 [DX5074]
S99-50217@FBGA64 [DX5074]
S99-50221@FBGA64 [DX5103]
S99-50222@FBGA64 [DX5103]
S99-50224@TSOP56 [DX1011]
S99-50251@FBGA64 [DX5103]
S99-50268@FBGA64 [DX5103]
S99-50282@FBGA64 [DX5103]
S99-50291@FBGA64 [DX5103]
S99GL128S0110@FBGA64 [DX5074]
S99PL127J004@TSOP56 [DX1011]
S99PL128JC0BAWFC0@FBGA84 [DX5001]
S99PL128JC0BAWNB0@FBGA84 [DX5001]
S99PL128JC0BAWT10@FBGA84 [DX5001]
S99PL128JC0BAWUB0@FBGA84 [DX5001]
S99PL193JB0BAEFC@FBGA73 [DX5072]
S99PL193JB0BAEUC@FBGA73 [DX5072]
S99PL193JB0BAWFC@FBGA73 [DX5072]
S99PL193JB0BAWUC@FBGA73 [DX5072]
S99PL193JC0BAEFC@FBGA73 [DX5072]
S99PL193JC0BAEUC@FBGA73 [DX5072]
S99PL193JC0BAWFC@FBGA73 [DX5072]
S99PL193JC0BAWUC@FBGA73 [DX5072]

MICROCONTROLLER

MB90F038APF [DX3022]
MB90F038APMC [DX3021]
MB90F038ASPF [DX3022]
MB90F038ASPMC [DX3021]
MB90F038CAPF [DX3022]
MB90F038CAPMC [DX3021]
MB90F038CASPF [DX3022]
MB90F038CASPMC [DX3021]
MB90F038CSPF [DX3022]
MB90F038CSPMC [DX3021]
MB90F038SPF [DX3022]
MB90F038SPMC [DX3021]
MB91F59ACHPB [DX5263]
MB91F59ACHSPB [DX5263]
MB91F59ACPB [DX5263]
MB91F59ACSPB [DX5263]
MB91F59BCHPB [DX5263]
MB91F59BCHSPB [DX5263]
MB91F59BCPB [DX5263]
MB91F59BCSPB [DX5263]
MB95F694K@QFN48(parallel) [DX4021]
MB95F694K@QFP48(parallel) [DX3007]
MB95F694K@QFP52(parallel) [DX3010]
MB95F696K@QFN48(parallel) [DX4021]
MB95F696K@QFP48(parallel) [DX3007]
MB95F696K@QFP52(parallel) [DX3010]
MB95F698K@QFN48(parallel) [DX4021]
MB95F698K@QFP48(parallel) [DX3007]
MB95F698K@QFP52(parallel) [DX3010]
MB95F876K@QFP48(parallel) [DX3007]
MB95F876K@QFP52(parallel) [DX3010]
MB96F673AAPMC [DX3064]
MB96F673AAPMC1 [DX3011]
MB96F673ABPMC [DX3064]
MB96F673ABPMC1 [DX3011]
MB96F673RAPMC [DX3064]
MB96F673RAPMC1 [DX3011]
MB96F673RBPMC [DX3064]
MB96F673RBPMC1 [DX3011]
MB96F675AAPMC [DX3064]
MB96F675AAPMC1 [DX3011]
MB96F675ABPMC [DX3064]
MB96F675ABPMC1 [DX3011]
MB96F675RAPMC [DX3064]
MB96F675RAPMC1 [DX3011]
MB96F675RBPMC [DX3064]
MB96F675RBPMC1 [DX3011]
MB96F683AAPMC [DX3016]
MB96F683ABPMC [DX3016]
MB96F683RAPMC [DX3016]
MB96F683RBPMC [DX3016]
MB96F685AAPMC [DX3016]
MB96F685ABPMC [DX3016]
MB96F685RAPMC [DX3016]
MB96F685RBPMC [DX3016]
MB9BF218@QFP144 [DX3051]

SPANSION-CUSTOME

E(E)PROM/FRAM/NVRAM

S34ML01G200TFI00(MSTAR)@TSOP48 [DX1004-1]
S34ML01G200TFI00(SBM)@TSOP48 [DX1004-1]

SPANSION-CUSTOMER

E(E)PROM/FRAM/NVRAM

52H70@FBGA88 [DX5001]
S34ML01G100(ST7163)@TSOP48 [DX1004]
S34ML01G100BHI00(StarTimes) [DX5046]
S34ML01G100TFI00(9260)@TSOP48 [DX1004-1]
S34ML01G100TFI00(9G25)@TSOP48 [DX1004-1]
S34ML01G200TFI00(ST273)@TSOP48 [DX1004-3]
S34ML02G100TFI00(XY)@TSOP48 [DX1004-1]
S34ML02G100TFI00(ZK)@TSOP48 [DX1004-1]
S34ML02G200TFI(ST273)@TSOP48 [DX1004-3]
S34ML04G200TFI00(HW)@TSOP48 [DX1004-1]

SSSC

MICROCONTROLLER

SSU7301 [DX0001]
SSU7301@PLCC44 [DX2044]
SSU7301@TQFP44 [DX3002]

SST

E(E)PROM/FRAM/NVRAM

SST25LF010@SOIC8(4.0) [DX1045-1]
SST25LF010@SOIC8(5.4) [DX1044-1]
SST25LF010@WSON8 [DX4005-1]
SST25LF010A@SOIC8(4.0) [DX1045-1]
SST25LF010A@SOIC8(5.4) [DX1044-1]
SST25LF010A@WSON8 [DX4005-1]
SST25LF016A@SOIC8(4.0) [DX1045#1]
SST25LF016A@SOIC8(5.4) [DX1044#1]
SST25LF016A@WSON8 [DX4005#1]
SST25LF016B@SOIC8(4.0) [DX1045#1]
SST25LF016B@SOIC8(5.4) [DX1044#1]
SST25LF016B@WSON8 [DX4005#1]
SST25LF020@SOIC8(4.0) [DX1045-1]
SST25LF020@SOIC8(5.4) [DX1044-1]
SST25LF020@WSON8 [DX4005-1]
SST25LF020A@SOIC8(4.0) [DX1045-1]
SST25LF020A@SOIC8(5.4) [DX1044-1]
SST25LF020A@WSON8 [DX4005-1]
SST25LF040@SOIC8(4.0) [DX1045-1]
SST25LF040@SOIC8(5.4) [DX1044-1]
SST25LF040@WSON8 [DX4005-1]
SST25LF040A@SOIC8(4.0) [DX1045-1]
SST25LF040A@SOIC8(5.4) [DX1044-1]
SST25LF040A@WSON8 [DX4005-1]
SST25LF080@SOIC8(4.0) [DX1045-1]
SST25LF080@SOIC8(5.4) [DX1044-1]
SST25LF080@WSON8 [DX4005-1]
SST25LF080A@SOIC8(4.0) [DX1045-1]
SST25LF080A@SOIC8(5.4) [DX1044-1]

SST25LF080A@WSON8 [DX4005-1]
SST25PF020B@SOIC8 [DX1045#1]
SST25PF020B@USON8 [DX4002#1]
SST25PF020B@WSON8 [DX4005#1]
SST25PF040B@SOIC8[150mil] [DX1045#1]
SST25PF040B@SOIC8[200mil] [DX1044#1]
SST25PF040B@WSON8 [DX4005#1]
SST25PF080B@SOIC8[150mil] [DX1045#1]
SST25PF080B@SOIC8[200mil] [DX1044#1]
SST25PF080B@WSON8 [DX4005#1]
SST25VF010@SOIC8(4.0) [DX1045-1]
SST25VF010@SOIC8(5.4) [DX1044-1]
SST25VF010@WSON8 [DX4005-1]
SST25VF010A@SOIC8(4.0) [DX1045-1]
SST25VF010A@SOIC8(5.4) [DX1044-1]
SST25VF010A@WSON8 [DX4005-1]
SST25VF016B@SOIC8(4.0) [DX1045#1]
SST25VF016B@SOIC8(5.4) [DX1044#1]
SST25VF016B@WSON8 [DX4005#1]
SST25VF020@SOIC8(4.0) [DX1045-1]
SST25VF020@SOIC8(5.4) [DX1044-1]
SST25VF020@WSON8 [DX4005-1]
SST25VF020B@SOIC8(4.0) [DX1045#1]
SST25VF020B@SOIC8(5.4) [DX1044#1]
SST25VF020B@WSON8 [DX4005#1]
SST25VF032B@SOIC16 [DX1033#1]
SST25VF032B@SOIC8(4.0) [DX1045#1]
SST25VF032B@SOIC8(5.4) [DX1044#1]
SST25VF032B@WSON8 [DX4005#1]
SST25VF040@SOIC8(4.0) [DX1045-1]
SST25VF040@SOIC8(5.4) [DX1044-1]
SST25VF040@WSON8 [DX4005-1]
SST25VF040B@SOIC8(4.0) [DX1045#1]
SST25VF040B@SOIC8(5.4) [DX1044#1]
SST25VF040B@WSON8 [DX4005#1]
SST25VF064C@SOIC16 [DX1033#1]
SST25VF064C@SOIC8 [DX1044#1]
SST25VF064C@WSON8 [DX4006#1]
SST25VF080@SOIC8(4.0) [DX1045-1]
SST25VF080@SOIC8(5.4) [DX1044-1]
SST25VF080@WSON8 [DX4005-1]
SST25VF080B@SOIC8(4.0) [DX1045#1]
SST25VF080B@SOIC8(5.4) [DX1044#1]
SST25VF080B@WSON8 [DX4005#1]
SST25VF512@SOIC8(4.0) [DX1045-1]
SST25VF512@SOIC8(5.4) [DX1044-1]
SST25VF512@WSON8 [DX4005-1]
SST25VF512A@SOIC8(4.0) [DX1045-1]
SST25VF512A@SOIC8(5.4) [DX1044-1]
SST25VF512A@WSON8 [DX4005-1]
SST25WF010@SOIC8(4.0) [DX1045-1]
SST25WF010@SOIC8(5.4) [DX1044-1]
SST25WF010@WSON8 [DX4005-1]
SST25WF020@SOIC8(4.0) [DX1045-1]
SST25WF020@SOIC8(5.4) [DX1044-1]
SST25WF020@WSON8 [DX4005-1]
SST25WF040@SOIC8(4.0) [DX1045-1]
SST25WF040@SOIC8(5.4) [DX1044-1]
SST25WF040@WSON8 [DX4005-1]
SST25WF080@SOIC8(4.0) [DX1045-1]
SST25WF080@SOIC8(5.4) [DX1044-1]
SST25WF080@WSON8 [DX4005-1]
SST25WF512@SOIC8(4.0) [DX1045-1]
SST25WF512@SOIC8(5.4) [DX1044-1]
SST25WF512@WSON8 [DX4005-1]
SST26VF016@SOIC8 [DX1044#1]
SST26VF016@WSON8 [DX4005#1]
SST26VF016B@SOIC8 [DX1045#1]
SST26VF016B@SOIJ8 [DX1044#1]
SST26VF016B@WDFN8 [DX4005#1]
SST26VF032@SOIC8[150 mil] [DX1045#1]
SST26VF032@SOIC8[200 mil] [DX1044#1]

SST26VF032@WSON8 [DX4005#1]
SST26VF032B@SOIC8 [DX1044#1]
SST26VF032B@SOIJ8 [DX1045#1]
SST26VF032B@TFBGA24 [DX5157]
SST26VF032B@WDFN8 [DX4005#1]
SST26VF032BA@SOIJ8 [DX1045#1]
SST26VF032BA@WDFN8 [DX4005#1]
SST26WF016B@SOIC8 [DX1045#1]
SST26WF016B@WDFN8 [DX4005#1]
SST26WF016BA@SOIC8 [DX1045#1]
SST26WF016BA@WDFN8 [DX4005#1]
SST26WF040B@SOIC8 [DX1045#1]
SST26WF040B@USON8 [DX4002#1]
SST26WF040B@WDFN8 [DX4005#1]
SST26WF040BA@SOIC8 [DX1045#1]
SST26WF040BA@USON8 [DX4002#1]
SST26WF040BA@WDFN8 [DX4005#1]
SST26WF080B@SOIC8 [DX1045#1]
SST26WF080B@USON8 [DX4002#1]
SST26WF080B@WDFN8 [DX4005#1]
SST26WF080BA@SOIC8 [DX1045#1]
SST26WF080BA@USON8 [DX4002#1]
SST26WF080BA@WDFN8 [DX4005#1]
SST27SF010 [DX0001]
SST27SF010@PLCC32 [DX2032]
SST27SF010@TSOP32 [DX1002]
SST27SF020 [DX0001]
SST27SF020@PLCC32 [DX2032]
SST27SF020@TSOP32 [DX1002]
SST27SF256 [DX0001]
SST27SF256@PLCC32 [DX2032]
SST27SF256@VSOP32 [DX1003]
SST27SF512 [DX0001]
SST27SF512@PLCC32 [DX2032]
SST27SF512@VSOP32 [DX1003]
SST27VF010 [DX0001]
SST27VF010@PLCC32 [DX2032]
SST27VF010@TSOP32 [DX1002]
SST27VF020 [DX0001]
SST27VF020@PLCC32 [DX2032]
SST27VF020@TSOP32 [DX1002]
SST27VF040 [DX0001]
SST27VF040@PLCC32 [DX2032]
SST27VF040@TSOP32 [DX1002]
SST27VF256 [DX0001]
SST27VF256@PLCC32 [DX2032]
SST27VF256@VSOP32 [DX1003]
SST27VF512 [DX0001]
SST27VF512@PLCC32 [DX2032]
SST27VF512@VSOP32 [DX1003]
SST28EE011 [DX0001]
SST28EE011@PLCC32 [DX2032]
SST28EE011@TSOP32 [DX1002]
SST28LE011 [DX0001]
SST28LE011@PLCC32 [DX2032]
SST28LE011@TSOP32 [DX1002]
SST28LF040 [DX0001]
SST28LF040@PLCC32 [DX2032]
SST28LF040@TSOP32 [DX1002]
SST28SF040 [DX0001]
SST28SF040@PLCC32 [DX2032]
SST28SF040@TSOP32 [DX1002]
SST28SF040A [DX0001]
SST28SF040A@PLCC32 [DX2032]
SST28SF040A@TSOP32 [DX1002]
SST28VE011 [DX0001]
SST28VE011@PLCC32 [DX2032]
SST28VE011@TSOP32 [DX1002]
SST28VF040 [DX0001]
SST28VF040@PLCC32 [DX2032]
SST28VF040@TSOP32 [DX1002]
SST28VF040A [DX0001]
SST28VF040A@PLCC32 [DX2032]
SST28VF040A@TSOP32 [DX1002]
SST29EE010 [DX0001]
SST29EE010@PLCC32 [DX2032]
SST29EE010@TSOP32 [DX1002]
SST29EE010@VSOP32 [DX1003]
SST29EE020 [DX0001]
SST29EE020@PLCC32 [DX2032]
SST29EE020@TSOP32 [DX1002]
SST29EE020@VSOP32 [DX1003]
SST29EE512 [DX0001]
SST29EE512@PLCC32 [DX2032]
SST29EE512@TSOP32 [DX1002]
SST29EE512@VSOP32 [DX1003]
SST29LE010 [DX0001]
SST29LE010@PLCC32 [DX2032]
SST29LE010@TSOP32 [DX1002]
SST29LE010@VSOP32 [DX1003]
SST29LE020 [DX0001]
SST29LE020@PLCC32 [DX2032]
SST29LE020@TSOP32 [DX1002]
SST29LE020@VSOP32 [DX1003]
SST29LE512 [DX0001]
SST29LE512@PLCC32 [DX2032]

SST29LE512@TSOP32 [DX1002]
SST29LE512@VSOP32 [DX1003]
SST29SF010 [DX0001]
SST29SF010@PLCC32 [DX2032]
SST29SF010@VSOP32 [DX1003]
SST29SF020 [DX0001]
SST29SF020@PLCC32 [DX2032]
SST29SF020@VSOP32 [DX1003]
SST29SF040 [DX0001]
SST29SF040@PLCC32 [DX2032]
SST29SF040@VSOP32 [DX1003]
SST29SF512 [DX0001]
SST29SF512@PLCC32 [DX2032]
SST29SF512@VSOP32 [DX1003]
SST29VE010 [DX0001]
SST29VE010@PLCC32 [DX2032]
SST29VE010@TSOP32 [DX1002]
SST29VE010@VSOP32 [DX1003]
SST29VE020 [DX0001]
SST29VE020@PLCC32 [DX2032]
SST29VE020@TSOP32 [DX1002]
SST29VE020@VSOP32 [DX1003]
SST29VE512 [DX0001]
SST29VE512@PLCC32 [DX2032]
SST29VE512@TSOP32 [DX1002]
SST29VE512@VSOP32 [DX1003]
SST29VF010 [DX0001]
SST29VF010@PLCC32 [DX2032]
SST29VF010@VSOP32 [DX1003]
SST29VF020 [DX0001]
SST29VF020@PLCC32 [DX2032]
SST29VF020@VSOP32 [DX1003]
SST29VF040 [DX0001]
SST29VF040@PLCC32 [DX2032]
SST29VF040@VSOP32 [DX1003]
SST29VF512 [DX0001]
SST29VF512@PLCC32 [DX2032]
SST29VF512@VSOP32 [DX1003]
SST31LF021@VSOP32 [DX1003]
SST31LF021E@VSOP32 [DX1003]
SST31LF041@TSOP40 [DX1005]
SST31LF041A@VSOP32 [DX1003]
SST31LF043@TSOP40 [DX1005]
SST31LF043A@VSOP32 [DX1003]
SST32HF162@LFBGA48 [DX5004]
SST32HF162@TSOP48 [DX1004]
SST32HF1621C@LFBGA62 [DX5005]
SST32HF1621C@LFBGA63 [DX5005]
SST32HF1622C@LFBGA62 [DX5005]
SST32HF1622C@LFBGA63 [DX5005]
SST32HF164@LFBGA48 [DX5004]
SST32HF164@TSOP48 [DX1004]
SST32HF1641@LFBGA62 [DX5005]
SST32HF1641@LFBGA63 [DX5005]
SST32HF1641C@LFBGA62 [DX5005]
SST32HF1641C@LFBGA63 [DX5005]
SST32HF1642@FBGA62 [DX5005]
SST32HF1642@FBGA63 [DX5005]
SST32HF1642C@FBGA62 [DX5005]
SST32HF1642C@FBGA63 [DX5005]
SST32HF1681@LFBGA62 [DX5005]
SST32HF1681@LFBGA63 [DX5005]
SST32HF1682@LFBGA62 [DX5005]
SST32HF1682@LFBGA63 [DX5005]
SST32HF200@LFBGA48 [DX5002]
SST32HF201@LFBGA48 [DX5002]
SST32HF202@LFBGA48 [DX5002]
SST32HF324@LFBGA62 [DX5005]
SST32HF324@LFBGA63 [DX5005]
SST32HF324@TFBGA63 [DX5005]
SST32HF3241@LFBGA62 [DX5005]
SST32HF3241@LFBGA63 [DX5005]
SST32HF3241C@LFBGA62 [DX5005]
SST32HF3241C@LFBGA63 [DX5005]
SST32HF3242@FBGA62 [DX5005]
SST32HF3242@FBGA63 [DX5005]
SST32HF3242C@FBGA62 [DX5005]
SST32HF3242C@FBGA63 [DX5005]
SST32HF3244C@FBGA56 [DX5005]
SST32HF324C@LFBGA62 [DX5005]
SST32HF324C@LFBGA63 [DX5005]
SST32HF324C@TFBGA63 [DX5005]
SST32HF328@LFBGA62 [DX5005]
SST32HF328@LFBGA63 [DX5005]
SST32HF328@TFBGA63 [DX5005]
SST32HF3281@LFBGA62 [DX5005]
SST32HF3281@LFBGA63 [DX5005]
SST32HF3281C@LFBGA62 [DX5005]
SST32HF3281C@LFBGA63 [DX5005]
SST32HF3282@FBGA62 [DX5005]
SST32HF3282@FBGA63 [DX5005]
SST32HF3282C@FBGA62 [DX5005]
SST32HF3282C@FBGA63 [DX5005]
SST32HF3284@FBGA56 [DX5005]
SST32HF328C@LFBGA62 [DX5005]
SST32HF328C@LFBGA63 [DX5005]

SST32HF328C@TFBGA63 [DX5005]
SST32HF32A1@LFBGA63 [DX5005]
SST32HF400@LFBGA48 [DX5002]
SST32HF402@LFBGA48 [DX5002]
SST32HF64161@LFBGA64 [DX5005]
SST32HF64161C@LFBGA64 [DX5005]
SST32HF6481@LFBGA64 [DX5005]
SST32HF6481C@LFBGA64 [DX5005]
SST32HF6482@FBGA64 [DX5005]
SST32HF6482C@FBGA64 [DX5005]
SST32HF64A1@FBGA64 [DX5005]
SST32HF64A2@FBGA63 [DX5005]
SST32HF64B1@FBGA63 [DX5005]
SST32HF64B2@FBGA63 [DX5005]
SST32HF800@LFBGA48 [DX5002]
SST32HF802@LFBGA48 [DX5002]
SST34HF1601B@TSOP48 [DX1004]
SST34HF1601C@FBGA62 [DX5005]
SST34HF1602C@FBGA62 [DX5005]
SST34HF1621A@LFBGA56 [DX5005]
SST34HF1621C@FBGA56 [DX5005]
SST34HF1621S@FBGA56 [DX5005]
SST34HF1622C@FBGA56 [DX5005]
SST34HF1622S@FBGA56 [DX5005]
SST34HF162G@LBGA48 [DX5004]
SST34HF1641@LFBGA56 [DX5005]
SST34HF1641A@LFBGA62 [DX5005]
SST34HF1641C@FBGA62 [DX5005]
SST34HF1641D@FBGA62 [DX5005]
SST34HF1641J@FBGA62 [DX5005]
SST34HF1642@LFBGA56 [DX5005]
SST34HF1642C@FBGA62 [DX5005]
SST34HF1642D@FBGA62 [DX5005]
SST34HF164C@LBGA48 [DX5004]
SST34HF164G@LFBGA48 [DX5002]
SST34HF1681@LFBGA62 [DX5005]
SST34HF1681D@FBGA62 [DX5005]
SST34HF1681J@FBGA62 [DX5005]
SST34HF1682D@FBGA62 [DX5005]
SST34HF3243B@FBGA56 [DX5005]
SST34HF3243C@FBGA62 [DX5005]
SST34HF3244@FBGA62 [DX5005]
SST34HF3244C@FBGA62 [DX5005]
SST34HF3282@FBGA62 [DX5005]
SST34HF3283@FBGA62 [DX5005]
SST34HF3284@FBGA62 [DX5005]
SST34HF32A4@FBGA62 [DX5005]
SST34WA1602@FBGA44 [DX5099]
SST32HF32A1@LFBGA62 [DX5005]
SST32HF32A4@FBGA56 [DX5005]
SST32HF401@LFBGA48 [DX5002]
SST32HF64161@LFBGA63 [DX5005]
SST32HF64161C@LFBGA63 [DX5005]
SST32HF6481@LFBGA63 [DX5005]
SST32HF6481C@LFBGA63 [DX5005]
SST32HF6482@FBGA63 [DX5005]
SST32HF6482C@FBGA63 [DX5005]
SST32HF64A1@FBGA63 [DX5005]
SST32HF64A2@FBGA56 [DX5005]
SST32HF64A2@FBGA64 [DX5005]
SST32HF64B1@FBGA64 [DX5005]
SST32HF64B2@FBGA64 [DX5005]
SST32HF802@LBGA48 [DX5004]
SST34HF1601B@LFBGA56 [DX5005]
SST34HF1601C@FBGA56 [DX5005]
SST34HF1602C@FBGA56 [DX5005]
SST34HF1621@LFBGA56 [DX5005]
SST34HF1621A@LFBGA62 [DX5005]
SST34HF1621C@FBGA62 [DX5005]
SST34HF1622@LFBGA56 [DX5005]
SST34HF1622C@FBGA62 [DX5005]
SST34HF162C@LBGA48 [DX5004]
SST34HF162G@LFBGA48 [DX5002]
SST34HF1641A@LFBGA56 [DX5005]
SST34HF1641C@FBGA56 [DX5005]
SST34HF1641D@FBGA56 [DX5005]
SST34HF1641J@FBGA56 [DX5005]
SST34HF1641S@FBGA56 [DX5005]
SST34HF1642C@FBGA56 [DX5005]
SST34HF1642D@FBGA56 [DX5005]
SST34HF1642S@FBGA56 [DX5005]
SST34HF164G@LBGA48 [DX5004]
SST34HF1681@LFBGA56 [DX5005]
SST34HF1681D@FBGA56 [DX5005]
SST34HF1681J@FBGA56 [DX5005]
SST34HF1682D@FBGA56 [DX5005]
SST34HF3223B@FBGA56 [DX5005]
SST34HF3243C@FBGA56 [DX5005]
SST34HF3244@FBGA56 [DX5005]
SST34HF3244C@FBGA56 [DX5005]
SST34HF3282@FBGA56 [DX5005]
SST34HF3283@FBGA56 [DX5005]
SST34HF3284@FBGA56 [DX5005]
SST34HF32A4@FBGA56 [DX5005]
SST34WA1601@FBGA44 [DX5099]

SST36VF1601(B3K)@TFBGA48 [DX5002]
SST36VF1601(BK)@TFBGA48 [DX5005]
SST36VF1601@TSOP48 [DX1004]
SST36VF1601C@FBGA48 [DX5002]
SST36VF1601C@TSOP48 [DX1004]
SST36VF1601E@FBGA48 [DX5002]
SST36VF1601E@TSOP48 [DX1004]
SST36VF1601G@FBGA48 [DX5002]
SST36VF1601G@FBGA56 [DX5005]
SST36VF1601G@TSOP48 [DX1004]
SST36VF1602(B3K)@TFBGA48 [DX5002]
SST36VF1602(BK)@TFBGA48 [DX5005]
SST36VF1602@TSOP48 [DX1004]
SST36VF1602C@FBGA48 [DX5002]
SST36VF1602C@TSOP48 [DX1004]
SST36VF1602E@FBGA48 [DX5002]
SST36VF1602E@TSOP48 [DX1004]
SST36VF1602G@FBGA48 [DX5002]
SST36VF1602G@FBGA56 [DX5005]
SST36VF1602G@TSOP48 [DX1004]
SST36VF3203@FBGA48 [DX5002]
SST36VF3203@TSOP48 [DX1004]
SST36VF3204@FBGA48 [DX5002]
SST36VF3204@TSOP48 [DX1004]
SST37VF010 [DX0001]
SST37VF010@PLCC32 [DX2032]
SST37VF010@VSOP32 [DX1003]
SST37VF020 [DX0001]
SST37VF020@PLCC32 [DX2032]
SST37VF020@VSOP32 [DX1003]
SST37VF040 [DX0001]
SST37VF040@PLCC32 [DX2032]
SST37VF040@VSOP32 [DX1003]
SST37VF512 [DX0001]
SST37VF512@PLCC32 [DX2032]
SST37VF512@VSOP32 [DX1003]
SST38UF166@TSOP48 [DX1004]
SST38VF166@TSOP48 [DX1004]
SST38VF6401@FBGA48 [DX5002]
SST38VF6401@TSOP48 [DX1004]
SST38VF6401B@FBGA48 [DX5002]
SST38VF6401B@TSOP48 [DX1004]
SST38VF6402@FBGA48 [DX5002]
SST38VF6402@TSOP48 [DX1004]
SST38VF6402B@FBGA48 [DX5002]
SST38VF6402B@TSOP48 [DX1004]
SST38VF6403@FBGA48 [DX5002]
SST38VF6403@TSOP48 [DX1004]
SST38VF6403B@FBGA48 [DX5002]
SST38VF6403B@TSOP48 [DX1004]
SST38VF6404@FBGA48 [DX5002]
SST38VF6404@TSOP48 [DX1004]
SST38VF6404B@FBGA48 [DX5002]
SST38VF6404B@TSOP48 [DX1004]
SST39LF010@PLCC32 [DX2032]
SST39LF010@TFBGA48 [DX5002]
SST39LF010@VSOP32 [DX1003]
SST39LF010@WFBGA34 [DX5037]
SST39LF016@FBGA48 [DX5002]
SST39LF016@TSOP40 [DX1006]
SST39LF020@PLCC32 [DX2032]
SST39LF020@TFBGA48 [DX5002]
SST39LF020@VSOP32 [DX1003]
SST39LF020@WFBGA34 [DX5037]
SST39LF040@PLCC32 [DX2032]
SST39LF040@TFBGA48 [DX5002]
SST39LF040@VSOP32 [DX1003]
SST39LF080@FBGA48 [DX5002]
SST39LF080@TSOP40 [DX1006]
SST39LF080Q@TSOP40 [DX1006]
SST39LF100@FBGA48 [DX5002]
SST39LF100@VSOP40 [DX1005]
SST39LF160(B2)@TFBGA48 [DX5002]
SST39LF160@TFBGA48 [DX5005]
SST39LF160@TSOP48 [DX1004]
SST39LF200@TFBGA48 [DX5005]
SST39LF200@TSOP48 [DX1043]
SST39LF200A(B2/B3)@TFBGA48 [DX5002]
SST39LF200A@TFBGA48 [DX5005]
SST39LF200A@TSOP48 [DX1043]
SST39LF200A@WFBGA48 [DX5037]
SST39LF400@TFBGA48 [DX5005]
SST39LF400@TSOP48 [DX1043]
SST39LF400A(B2/B3)@TFBGA48 [DX5002]
SST39LF400A@TFBGA48 [DX5005]
SST39LF400A@TSOP48 [DX1043]
SST39LF400A@WFBGA48 [DX5037]
SST39LF512@PLCC32 [DX2032]
SST39LF512@VSOP32 [DX1003]
SST39LF800@TFBGA48 [DX5005]

SST39LF800@TSOP48 [DX1004]
SST39LF800A(B2/B3)@TFBGA48 [DX5002]
SST39LF800A@TFBGA48 [DX5005]
SST39LF800A@TSOP48 [DX1004]
SST39LF800A@WFBGA48 [DX5037]
SST39LF801C@@TFBGA48 [DX5002]
SST39LF801C@@TSOP48 [DX1004]
SST39LF801C@@WFBGA48 [DX5038]
SST39LF802C@@TFBGA48 [DX5002]
SST39LF802C@@TSOP48 [DX1004]
SST39LF802C@@WFBGA48 [DX5038]
SST39LH010 [DX0001]
SST39LH010@PLCC32 [DX2032]
SST39LH010@TSOP32 [DX1002]
SST39LH040 [DX0001]
SST39LH040@PLCC32 [DX2032]
SST39LH040@TSOP32 [DX1002]
SST39LH512 [DX0001]
SST39LH512@PLCC32 [DX2032]
SST39LH512@TSOP32 [DX1002]
SST39SF010 [DX0001]
SST39SF010@PLCC32 [DX2032]
SST39SF010@VSOP32 [DX1003]
SST39SF010A [DX0001]
SST39SF010A@PLCC32 [DX2032]
SST39SF010A@VSOP32 [DX1003]
SST39SF020 [DX0001]
SST39SF020@PLCC32 [DX2032]
SST39SF020@VSOP32 [DX1003]
SST39SF020A [DX0001]
SST39SF020A@PLCC32 [DX2032]
SST39SF020A@VSOP32 [DX1003]
SST39SF020P [DX0001]
SST39SF020P@PLCC32 [DX2032]
SST39SF020P@VSOP32 [DX1003]
SST39SF040 [DX0001]
SST39SF040@PLCC32 [DX2032]
SST39SF040@VSOP32 [DX1003]
SST39SF040P [DX0001]
SST39SF040P@PLCC32 [DX2032]
SST39SF040P@VSOP32 [DX1003]
SST39SF512 [DX0001]
SST39SF512@PLCC32 [DX2032]
SST39SF512@VSOP32 [DX1003]
SST39SF512A [DX0001]
SST39SF512A@PLCC32 [DX2032]
SST39SF512A@VSOP32 [DX1003]
SST39VF010 [DX0001]
SST39VF010@PLCC32 [DX2032]
SST39VF010@TFBGA48 [DX5002]
SST39VF010@VSOP32 [DX1003]
SST39VF016@FBGA48 [DX5002]
SST39VF016@TSOP40 [DX1006]
SST39VF016Q@TSOP40 [DX1006]
SST39VF020 [DX0001]
SST39VF020@PLCC32 [DX2032]
SST39VF020@TFBGA48 [DX5002]
SST39VF020@VSOP32 [DX1003]
SST39VF020P [DX0001]
SST39VF020P@PLCC32 [DX2032]
SST39VF020P@VSOP32 [DX1003]
SST39VF040 [DX0001]
SST39VF040@PLCC32 [DX2032]
SST39VF040@TFBGA48 [DX5002]
SST39VF040@VSOP32 [DX1003]
SST39VF040P [DX0001]
SST39VF040P@PLCC32 [DX2032]
SST39VF040P@VSOP32 [DX1003]
SST39VF080@FBGA48 [DX5002]
SST39VF080@TSOP40 [DX1006]
SST39VF080Q@TSOP40 [DX1006]
SST39VF088@TSOP48 [DX1004]
SST39VF100@FBGA48 [DX5002]
SST39VF100@VSOP40 [DX1005]
SST39VF160(B2)@TFBGA48 [DX5002]
SST39VF160@TFBGA48 [DX5005]
SST39VF160@TSOP48 [DX1004]
SST39VF160@TSOP48(SLOW) [DX1043]
SST39VF1601@TFBGA48 [DX5002]
SST39VF1601@TSOP48 [DX1004]
SST39VF1601C@FBGA48 [DX5002]
SST39VF1601C@TSOP48 [DX1004]
SST39VF1602@TFBGA48 [DX5002]
SST39VF1602@TSOP48 [DX1004]
SST39VF1602C@FBGA48 [DX5002]
SST39VF1602C@TSOP48 [DX1004]
SST39VF160Q@TSOP48 [DX1004]
SST39VF1681@TFBGA48 [DX5002]
SST39VF1681@TSOP48 [DX1004]
SST39VF1682@TFBGA48 [DX5002]
SST39VF1682@TSOP48 [DX1004]
SST39VF200A(B2/B3)@TFBGA48 [DX5002]

SST39VF200A@TFBGA48 [DX5005]
SST39VF200A@TSOP48 [DX1043]
SST39VF200A@WFBGA48 [DX5037]
SST39VF320@TFBGA48 [DX5002]
SST39VF320@TSOP48 [DX1004]
SST39VF3201@TFBGA48 [DX5002]
SST39VF3201@TSOP48 [DX1004]
SST39VF3201B@FBGA48 [DX5002]
SST39VF3201B@TSOP48 [DX1004]
SST39VF3201C@FBGA48 [DX5002]
SST39VF3201C@TSOP48 [DX1004]
SST39VF3202@TFBGA48 [DX5002]
SST39VF3202@TSOP48 [DX1004]
SST39VF3202B@FBGA48 [DX5002]
SST39VF3202B@TSOP48 [DX1004]
SST39VF3202C@FBGA48 [DX5002]
SST39VF3202C@TSOP48 [DX1004]
SST39VF400@TSOP48 [DX1043]
SST39VF400A(B2/B3)@TFBGA48 [DX5002]
SST39VF400A@TFBGA48 [DX5005]
SST39VF400A@TSOP48 [DX1043]
SST39VF400A@WFBGA48 [DX5037]
SST39VF400Q@TSOP48 [DX1043]
SST39VF512 [DX0001]
SST39VF512@PLCC32 [DX2032]
SST39VF512@VSOP32 [DX1003]
SST39VF6401@TFBGA48 [DX5005]
SST39VF6401@TSOP48 [DX1004]
SST39VF6401B@FBGA48 [DX5005]
SST39VF6401B@TSOP48 [DX1004]
SST39VF6402@TFBGA48 [DX5005]
SST39VF6402@TSOP48 [DX1004]
SST39VF6402B@FBGA48 [DX5005]
SST39VF6402B@TSOP48 [DX1004]
SST39VF800@TSOP48 [DX1004]
SST39VF800A(B2/B3)@TFBGA48 [DX5002]
SST39VF800A@TFBGA48 [DX5005]
SST39VF800A@TSOP48 [DX1004]
SST39VF800A@WFBGA48 [DX5037]
SST39VF800Q@TSOP48 [DX1004]
SST39VF801C@@TFBGA48 [DX5002]
SST39VF801C@@TSOP48 [DX1004]
SST39VF801C@@WFBGA48 [DX5038]
SST39VF802C@@TFBGA48 [DX5002]
SST39VF802C@@TSOP48 [DX1004]
SST39VF802C@@WFBGA48 [DX5038]
SST39WF1601D@FBGA48 [DX5002]
SST39WF1601D@WFBGA48 [DX5038]
SST39WF1602D@FBGA48 [DX5002]
SST39WF1602D@WFBGA48 [DX5038]
SST39WF400A(02)@TFBGA48 [DX5002]
SST39WF400A(02)@WFBGA48 [DX5037]
SST39WF400A(03)@TFBGA48 [DX5002]
SST39WF400A(03)@WFBGA48 [DX5037]
SST39WF400B(M2)@WFBGA48 [DX5038]
SST39WF400B(Y1)@WFBGA48 [DX5038]
SST39WF400B@TFBGA48 [DX5002]
SST39WF800A(M2)@WFBGA48 [DX5038]
SST39WF800A(Y1)@WFBGA48 [DX5037]
SST39WF800A@TFBGA48 [DX5002]
SST39WF800B(M2)@WFBGA48 [DX5038]
SST39WF800B(Y1)@WFBGA48 [DX5037]
SST39WF800B@TFBGA48 [DX5002]
SST49LF002@PLCC32 [DX2032]
SST49LF002@VSOP32 [DX1003]
SST49LF002A@PLCC32 [DX2032]
SST49LF002A@VSOP32 [DX1003]
SST49LF002B@PLCC32 [DX2032]
SST49LF003A@PLCC32 [DX2032]
SST49LF003A@VSOP32 [DX1003]
SST49LF003B@PLCC32 [DX2032]
SST49LF004@PLCC32 [DX2032]
SST49LF004@VSOP32 [DX1003]
SST49LF004A@PLCC32 [DX2032]
SST49LF004A@VSOP32 [DX1003]
SST49LF004B@PLCC32 [DX2032]
SST49LF004B@VSOP32 [DX1003]
SST49LF004B@VSOP40 [DX1006]
SST49LF008@PLCC32 [DX2032]
SST49LF008@VSOP32 [DX1003]
SST49LF008A@PLCC32 [DX2032]
SST49LF008A@TSOP40 [DX1006]
SST49LF008A@VSOP32 [DX1003]
SST49LF020@PLCC32 [DX2032]
SST49LF020@VSOP32 [DX1003]
SST49LF020A@PLCC32 [DX2032]
SST49LF020A@VSOP32 [DX1003]
SST49LF030A@PLCC32 [DX2032]
SST49LF030A@VSOP32 [DX1003]
SST49LF040@PLCC32 [DX2032]
SST49LF040@VSOP32 [DX1003]
SST49LF040A@PLCC32 [DX2032]
SST49LF040A@VSOP32 [DX1003]
SST49LF040B@PLCC32 [DX2032]

SST49LF040B@TSOP40 [DX1006]
SST49LF040B@VSOP32 [DX1003]
SST49LF080A@PLCC32 [DX2032]
SST49LF080A@VSOP32 [DX1003]

MICROCONTROLLER

SST65P542R@SOIC28 [DX1033]
SST89C54 [DX0001]
SST89C54@PLCC44 [DX2044]
SST89C54@TQFP44 [DX3003]
SST89C58 [DX0001]
SST89C58@PLCC44 [DX2044]
SST89C58@TQFP44 [DX3003]
SST89C58RC@PLCC44 [DX2044]
SST89C58RC@QFN40 [DX4017]
SST89C58RC@TQFP44 [DX3003]
SST89E516RD [DX0001]
SST89E516RD@PLCC44 [DX2044]
SST89E516RD@TQFP44 [DX3003]
SST89E516RD2 [DX0001]
SST89E516RD2@PLCC44 [DX2044]
SST89E516RD2@TQFP44 [DX3003]
SST89E52RC [DX0001]
SST89E52RC@PLCC44 [DX2044]
SST89E52RC@TQFP44 [DX3003]
SST89E52RD [DX0001]
SST89E52RD@PLCC44 [DX2044]
SST89E52RD@TQFP44 [DX3003]
SST89E52RD2 [DX0001]
SST89E52RD2@PLCC44 [DX2044]
SST89E52RD2@TQFP44 [DX3003]
SST89E54RC [DX0001]
SST89E54RC@PLCC44 [DX2044]
SST89E54RC@TQFP44 [DX3003]
SST89E54RD [DX0001]
SST89E54RD@PLCC44 [DX2044]
SST89E54RD@TQFP44 [DX3003]
SST89E54RD2 [DX0001]
SST89E54RD2@PLCC44 [DX2044]
SST89E54RD2@TQFP44 [DX3003]
SST89E54RD2A [DX0001]
SST89E54RD2A@PLCC44 [DX2044]
SST89E54RD2A@TQFP44 [DX3003]
SST89E54RDA [DX0001]
SST89E54RDA@PLCC44 [DX2044]
SST89E54RDA@TQFP44 [DX3003]
SST89E554RC [DX0001]
SST89E554RC@PLCC44 [DX2044]
SST89E554RC@TQFP44 [DX3003]
SST89E564 [DX0001]
SST89E564@PLCC44 [DX2044]
SST89E564@TQFP44 [DX3003]
SST89E564RD [DX0001]
SST89E564RD@PLCC44 [DX2044]
SST89E564RD@TQFP44 [DX3003]
SST89E58RD [DX0001]
SST89E58RD@PLCC44 [DX2044]
SST89E58RD@TQFP44 [DX3003]
SST89E58RD2 [DX0001]
SST89E58RD2@PLCC44 [DX2044]
SST89E58RD2@TQFP44 [DX3003]
SST89E58RD2A [DX0001]
SST89E58RD2A@PLCC44 [DX2044]
SST89E58RD2A@TQFP44 [DX3003]
SST89E58RDA [DX0001]
SST89E58RDA@PLCC44 [DX2044]
SST89E58RDA@TQFP44 [DX3003]
SST89V516RD [DX0001]
SST89V516RD@PLCC44 [DX2044]
SST89V516RD@TQFP44 [DX3003]
SST89V516RD2 [DX0001]
SST89V516RD2@PLCC44 [DX2044]
SST89V516RD2@TQFP44 [DX3003]
SST89V52RD [DX0001]
SST89V52RD@PLCC44 [DX2044]
SST89V52RD@TQFP44 [DX3003]
SST89V52RD2 [DX0001]
SST89V52RD2@PLCC44 [DX2044]
SST89V52RD2@TQFP44 [DX3003]
SST89V54RD2 [DX0001]
SST89V54RD2@PLCC44 [DX2044]
SST89V54RD2@TQFP44 [DX3003]
SST89V554RC [DX0001]
SST89V554RC@PLCC44 [DX2044]
SST89V554RC@TQFP44 [DX3003]
SST89V564 [DX0001]
SST89V564@PLCC44 [DX2044]
SST89V564@TQFP44 [DX3003]
SST89V564RD [DX0001]
SST89V564RD@PLCC44 [DX2044]

SST89V564RD@TQFP44 [DX3003]
SST89V58RD2 [DX0001]
SST89V58RD2@PLCC44 [DX2044]
SST89V58RD2@TQFP44 [DX3003]

SST-CUSTOMER

E(E)PROM/FRAM/NVRAM

SST39SF010A@PLCC32 [DX2032]
SST39SF020A@PLCC32 [DX2032]

SSU

MICROCONTROLLER

SSU2C508 [DX0001]
SSU2C508N [DX0001]
SSU6C676 [DX0001]
SSU6C676@SOIC14 [DX1030]
SSU6C676@TSSOP14 [DX1000]
SSU6C73 [DX0001]
SSU6C74 [DX0001]

ST

E(E)PROM/FRAM/NVRAM

ET2716 [DX0001]
ETC2716 [DX0001]
ETC2732 [DX0001]
M13C02 [DX0001]
M13C02@SOIC8 [DX1045]
M24128 [DX0001]
M24128@MLP8 [DX4047]
M24128@SOIC8 [DX1045]
M24128@TSOP8 [DX1059]
M24164 [DX0001]
M24164@SOIC8 [DX1045]
M24256 [DX0001]
M24256@MLP8 [DX4047]
M24256@SOIC8[3.9] [DX1045]
M24256@SOIC8[5.5] [DX1044]
M24256@TSOP8 [DX1059]
M24256@WLCSP8 [DX0001]
M24256BF@MLP8 [DX4047]
M24256BF@SOIC8[3.9] [DX1045]
M24256BF@SOIC8[5.5] [DX1044]
M24256BF@TSOP8 [DX1059]
M24256BR [DX0001]
M24256BR@MLP8 [DX4047]
M24256BR@SOIC8[3.9] [DX1045]
M24256BR@SOIC8[5.5] [DX1044]
M24256BR@TSOP8 [DX1059]
M24256BW [DX0001]
M24256BW@MLP8 [DX4047]
M24256BW@SOIC8[3.9] [DX1045]
M24256BW@SOIC8[5.5] [DX1044]
M24256BW@TSOP8 [DX1059]
M24512 [DX0001]
M24512@SOIC8(150 mil) [DX1045]
M24512@SOIC8(200 mil) [DX1044]
M24512@TSOP8 [DX1059]
M24C01 [DX0001]
M24C01@MLP8 [DX4047]
M24C01@SOIC8 [DX1045]
M24C01R [DX0001]
M24C01R@MLP8 [DX4047]
M24C01R@SOIC8 [DX1045]
M24C01R@TSOP8 [DX1059]
M24C01W [DX0001]
M24C01W@MLP8 [DX4047]
M24C01W@SOIC8 [DX1045]
M24C01W@TSOP8 [DX1059]

M24C02 [DX0001]
M24C02@MLP8 [DX4047]
M24C02@SOIC8 [DX1045]
M24C02R [DX0001]
M24C02R@MLP8 [DX4047]
M24C02R@SOIC8 [DX1045]
M24C02R@TSOP8 [DX1059]
M24C02W [DX0001]
M24C02W@MLP8 [DX4047]
M24C02W@SOIC8 [DX1045]
M24C02W@TSOP8 [DX1059]
M24C04 [DX0001]
M24C04@MLP8 [DX4047]
M24C04@SOIC8 [DX1045]
M24C04R [DX0001]
M24C04R@MLP8 [DX4047]
M24C04R@SOIC8 [DX1045]
M24C04R@TSOP8 [DX1059]
M24C04W [DX0001]
M24C04W@MLP8 [DX4047]
M24C04W@SOIC8 [DX1045]
M24C04W@TSOP8 [DX1059]
M24C08 [DX0001]
M24C08@MLP8 [DX4047]
M24C08@MSOP8 [DX4007]
M24C08@SOIC8 [DX1045]
M24C08@TSOP8 [DX1059]
M24C08R [DX0001]
M24C08R@MLP8 [DX4047]
M24C08R@MSOP8 [DX4007]
M24C08R@SOIC8 [DX1045]
M24C08R@TSOP8 [DX1059]
M24C08W [DX0001]
M24C08W@MLP8 [DX4047]
M24C08W@MSOP8 [DX4007]
M24C08W@SOIC8 [DX1045]
M24C08W@TSOP8 [DX1059]
M24C128(BN) [DX0001]
M24C128(MN)@SOIC8 [DX1044]
M24C128(MW)@SOIC8 [DX1045]
M24C128@MLP8 [DX4047]
M24C128B(BN) [DX0001]
M24C128B(MN)@SOIC8 [DX1044]
M24C128B(MW)@SOIC8 [DX1045]
M24C128B@MLP8 [DX4047]
M24C16 [DX0001]
M24C16@MLP8 [DX4047]
M24C16@SOIC8 [DX1045]
M24C16R [DX0001]
M24C16R@MLP8 [DX4047]
M24C16R@SOIC8 [DX1045]
M24C16R@TSOP8 [DX1059]
M24C16W [DX0001]
M24C16W@MLP8 [DX4047]
M24C16W@SOIC8 [DX1045]
M24C16W@TSOP8 [DX1059]
M24C256(BN) [DX0001]
M24C256(MN)@SOIC8 [DX1044]
M24C256(MW)@SOIC8 [DX1045]
M24C256@MLP8 [DX4047]
M24C256A(BN) [DX0001]
M24C256A(MN)@SOIC8 [DX1044]
M24C256A(MW)@SOIC8 [DX1045]
M24C256A@MLP8 [DX4047]
M24C256B(BN) [DX0001]
M24C256B(MN)@SOIC8 [DX1044]
M24C256B(MW)@SOIC8 [DX1045]
M24C256B@MLP8 [DX4047]
M24C256W(BN) [DX0001]
M24C256W(MN)@SOIC8 [DX1044]
M24C256W(MW)@SOIC8 [DX1045]
M24C256W@MLP8 [DX4047]
M24C32(BN) [DX0001]
M24C32(DL)@TSSOP14 [DX1000]
M24C32(DW)@TSSOP8 [DX1059]
M24C32(MN)@SOIC8 [DX1044]
M24C32(MW)@SOIC8 [DX1045]
M24C32@MLP8 [DX4047]
M24C32W(BN) [DX0001]
M24C32W(DL)@TSSOP14 [DX1000]
M24C32W(DW)@TSSOP8 [DX1059]
M24C32W(MN)@SOIC8 [DX1045]
M24C32W(MW)@SOIC8 [DX1044]
M24C32W@MLP8 [DX4047]
M24C64(BN) [DX0001]
M24C64(DL)@TSSOP14 [DX1000]
M24C64(DW)@TSSOP8 [DX1059]
M24C64(MN)@SOIC8 [DX1044]
M24C64(MW)@SOIC8 [DX1045]
M24C64@MLP8 [DX4047]
M24C64W(BN) [DX0001]
M24C64W(DL)@TSSOP14 [DX1000]
M24C64W(DW)@TSSOP8 [DX1059]
M24C64W(MN)@SOIC8 [DX1044]
M24C64W(MW)@SOIC8 [DX1045]
M24C64W@MLP8 [DX4047]

M24CL04B [DX0001]
M24CL04B@MLP8 [DX4047]
M24CL04B@SOIC8 [DX1045]
M24CL04B@TSOP8 [DX1059]
M24E16 [DX0001]
M24E32(BN) [DX0001]
M24E32(DW)@TSSOP8 [DX1059]
M24E32(MN)@SOIC8 [DX1044]
M24E32(MW)@SOIC8 [DX1045]
M24M01@LGA8 [DX4006]
M24M01@SOIC8 [DX1045]
M24M01-HR@SOIC8(150 mil) [DX1045]
M24M01-HR@SOIC8(200 mil) [DX1044]
M24M01-HR@WLCSP8 [DX0001]
M24M01-R@SOIC8(150 mil) [DX1045]
M24M01-R@SOIC8(200 mil) [DX1044]
M24M01-R@WLCSP8 [DX0001]
M24M01-W@SOIC8(150 mil) [DX1045]
M24M01-W@SOIC8(200 mil) [DX1044]
M24M01-W@WLCSP8 [DX0001]
M24W01 [DX0001]
M24W01@SOIC8 [DX1045]
M24W02 [DX0001]
M24W02@SOIC8 [DX1045]
M24W04 [DX0001]
M24W04@SOIC8 [DX1045]
M24W08 [DX0001]
M24W08@SOIC8 [DX1045]
M24W16 [DX0001]
M24W16@SOIC8 [DX1045]
M25C01 [DX0001]
M25C02 [DX0001]
M25C04 [DX0001]
M25C08 [DX0001]
M25C16 [DX0001]
M25E16 [DX0001]
M25P05@SOIC8 [DX1045]
M25P05@VQFPN8 [DX4005]
M25P05-A@SOIC8 [DX1045#1]
M25P05-A@TSSOP8 [DX1059#3]
M25P05-A@VDFPN8 [DX4005#1]
M25P10@SOIC8 [DX1045]
M25P10@UFDFPN8 [DX4002]
M25P10@VQFPN8 [DX4005]
M25P10-A@SOIC8 [DX1045#1]
M25P10-A@VFQFPN8 [DX4005#1]
M25P128@SOIC16 [DX1072#1]
M25P128@SOIC16(ISP) [DX0001]
M25P128@VDFPN8 [DX4006#1]
M25P128@VDFPN8(ISP) [DX0001]
M25P16@SOIC16 [DX1072#1]
M25P16@SOIC16(ISP) [DX0001]
M25P16@SOIC8(150mil) [DX1045#1]
M25P16@SOIC8(150mil)(ISP) [DX0001]
M25P16@SOIC8(200mil) [DX1044#1]
M25P16@SOIC8(200mil)(ISP) [DX0001]
M25P16@VDFPN8 [DX4006#1]
M25P16@VDFPN8(ISP) [DX0001]
M25P16@VFQFPN8 [DX4005#1]
M25P16@VFQFPN8(ISP) [DX0001]
M25P20@SOIC8 [DX1045#1]
M25P20@VFQFPN8 [DX4005#1]
M25P32(Fast Mode)@SOIC16 [DX1033#1]
M25P32(Fast Mode)@SOIC8(150mil) [DX1044#1]
M25P32(Fast Mode)@SOIC8(200mil) [DX4005#1]
M25P32(Fast Mode)@VQFPN8 [DX4006#1]
M25P32@SOIC16 [DX1072#1]
M25P32@SOIC16(ISP) [DX0001]
M25P32@SOIC8 [DX1044#1]
M25P32@SOIC8(ISP) [DX0001]
M25P32@VDFPN8 [DX4006#1]
M25P32@VDFPN8(ISP) [DX0001]
M25P32@VFQFPN8 [DX4005#1]
M25P32@VFQFPN8(ISP) [DX0001]
M25P40@SOIC8 [DX1045#1]
M25P40@VFQFPN8 [DX4005#1]
M25P64(Fast Mode)@SOIC16 [DX1033#1]
M25P64(Fast Mode)@VDFPN8 [DX4006#1]
M25P64@SOIC16 [DX1072#1]
M25P64@SOIC16(ISP) [DX0001]
M25P64@VDFPN8 [DX4006#1]
M25P64@VDFPN8(ISP) [DX0001]
M25P80@SOIC16 [DX1033#1]
M25P80@SOIC8 [DX1044#1]

M25P80@VFQFPN8 [DX4005#1]
M25PE10@SOIC8(ISP) [DX0001]
M25PE10@VQFPN8(ISP) [DX0001]
M25PE16@VQFPN8 [DX4005#1]
M25PE20@SOIC8(ISP) [DX0001]
M25PE20@VQFPN8(ISP) [DX0001]
M25PE40@SOIC8(ISP) [DX0001]
M25PE40@VQFPN8(ISP) [DX0001]
M25PE80@SOIC8(ISP) [DX0001]
M25PE80@VQFPN8(ISP) [DX0001]
M25PX32@SOIC8 [DX1044#1]
M25PX32@VFQFPN8 [DX4005#1]
M25PX64@TBGA24 [DX5157]
M25PX64@TBGA24(SKYWORTH) [DX5157]
M25PX64@VDFPN8 [DX4006#1]
M25W02 [DX0001]
M25W08 [DX0001]
M25W166 [DX0001]
M2716 [DX0001]
M27256 [DX0001]
M2732A [DX0001]
M2764 [DX0001]
M27C1000 [DX0001]
M27C1000@TSOP32 [DX1002]
M27C1001@PLCC32 [DX2032]
M27C1024 [DX0001]
M27C128B [DX0001]
M27C160 [DX0001]
M27C160@PSOP44 [DX1014]
M27C160K@PLCC44 [DX2044]
M27C2001 [DX0001]
M27C2001@TSOP32 [DX1002]
M27C202@PLCC44 [DX2044]
M27C256B [DX0001]
M27C32 [DX0001]
M27C322@SDIP42 [DX0042]
M27C4001 [DX0001]
M27C4001@TSOP32 [DX1002]
M27C4002@PLCC44 [DX2044]
M27C405@PLCC32 [DX2032]
M27C512 [DX0001]
M27C513 [DX0001]
M27C516@PLCC44 [DX2044]
M27C64A@PLCC32 [DX2032]
M27C800@PLCC44 [DX2044]
M27C801 [DX0001]
M27C801@TSOP32 [DX1002]
M27HC641@PLCC28 [DX2028]
M25PE10@SOIC8 [DX1045#1]
M25PE10@VQFPN8 [DX4005#1]
M25PE16@SOIC8 [DX1044#1]
M25PE20@SOIC8 [DX1045#1]
M25PE20@VQFPN8 [DX4005#1]
M25PE40@SOIC8 [DX1044#1]
M25PE40@VQFPN8 [DX4005#1]
M25PE80@SOIC8 [DX1044#1]
M25PE80@VQFPN8 [DX4005#1]
M25PX32@SOIC16 [DX1033#1]
M25PX32@TBGA24 [DX5157]
M25PX64@SOIC16 [DX1033#1]
M25W01 [DX0001]
M25W04 [DX0001]
M25W16 [DX0001]
M27128A [DX0001]
M2716F1 [DX0001]
M27256A [DX0001]
M27512 [DX0001]
M2764A [DX0001]
M27C1000@PLCC32 [DX2032]
M27C1001 [DX0001]
M27C1001@TSOP32 [DX1002]
M27C1024@PLCC44 [DX2044]
M27C16 [DX0001]
M27C160@PLCC44 [DX2044]
M27C160K [DX0001]
M27C160K@PSOP44 [DX1014]
M27C2001@PLCC32 [DX2032]
M27C202 [DX0001]
M27C202@VSOP40 [DX1005]
M27C256B@PLCC32 [DX2032]
M27C322 [DX0001]
M27C400 [DX0001]
M27C4001@PLCC32 [DX2032]
M27C4002 [DX0001]
M27C405 [DX0001]
M27C405@TSOP32 [DX1002]
M27C512@PLCC32 [DX2032]
M27C516 [DX0001]
M27C64A [DX0001]
M27C800 [DX0001]
M27C800@PSOP44 [DX1014]
M27C801@PLCC32 [DX2032]
M27HC641 [DX0001]
M27HC642 [DX0001]

M27HC642@PLCC28 [DX2028]
M27V101@PLCC32 [DX2032]
M27V102 [DX0001]
M27V160 [DX0001]
M27V160@PSOP44 [DX1014]
M27V160K@PLCC44 [DX2044]
M27V201 [DX0001]
M27V201@TSOP32 [DX1002]
M27V322 [DX0001]
M27V401 [DX0001]
M27V401@TSOP32 [DX1002]
M27V402@PLCC44 [DX2044]
M27V405 [DX0001]
M27V405@TSOP32 [DX1002]
M27V512@PLCC32 [DX2032]
M27V800 [DX0001]
M27V801 [DX0001]
M27V801@TSOP32 [DX1002]
M27W016@PSOP44 [DX1014]
M27W016@TSOP48 [DX1004]
M27W032@TSOP48 [DX1004]
M27W064@TSOP48 [DX1004]
M27W101@PLCC32 [DX2032]
M27W102 [DX0001]
M27W160 [DX0001]
M27W160@PSOP44 [DX1014]
M27W201@PLCC32 [DX2032]
M27W202 [DX0001]
M27W202@VSOP40 [DX1005]
M27W400@PLCC44 [DX2044]
M27W401@PLCC32 [DX2032]
M27W402 [DX0001]
M27W402@TSOP40 [DX1006]
M27W512@PLCC32 [DX2032]
M27W800 [DX0001]
M27W801 [DX0001]
M27W801@TSOP32 [DX1002]
M28010@PLCC32 [DX2032]
M28010R [DX0001]
M28010R@TSOP32 [DX1002]
M28010W@PLCC32 [DX2032]
M28256 [DX0001]
M28256@TSOP28 [DX1024]
M28C010@PLCC32 [DX2032]
M28C010R [DX0001]
M28C010R@TSOP32 [DX1002]
M28C010W@PLCC32 [DX2032]
M28C16@PLCC32 [DX2032]
M27V101 [DX0001]
M27V101@TSOP32 [DX1002]
M27V102@PLCC44 [DX2044]
M27V160@PLCC44 [DX2044]
M27V160K [DX0001]
M27V160K@PSOP44 [DX1014]
M27V201@PLCC32 [DX2032]
M27V256 [DX0001]
M27V322@SDIP42 [DX0042]
M27V401@PLCC32 [DX2032]
M27V402 [DX0001]
M27V402@TSOP40 [DX1006]
M27V405@PLCC32 [DX2032]
M27V512 [DX0001]
M27V512@TSOP28 [DX1024]
M27V800@PLCC44 [DX2044]
M27V801@PLCC32 [DX2032]
M27W016 [DX0001]
M27W016@SDIP42 [DX0042]
M27W032@PSOP44 [DX1014]
M27W064@PSOP44 [DX1014]
M27W101 [DX0001]
M27W101@TSOP32 [DX1002]
M27W102@PLCC44 [DX2044]
M27W160@PLCC44 [DX2044]
M27W201 [DX0001]
M27W201@TSOP32 [DX1002]
M27W202@PLCC44 [DX2044]
M27W400 [DX0001]
M27W401 [DX0001]
M27W401@TSOP32 [DX1002]
M27W402@PLCC44 [DX2044]
M27W512 [DX0001]
M27W512@TSOP28 [DX1024]
M27W800@PLCC44 [DX2044]
M27W801@PLCC32 [DX2032]
M28010 [DX0001]
M28010@TSOP32 [DX1002]
M28010R@PLCC32 [DX2032]
M28010W [DX0001]
M28010W@TSOP32 [DX1002]
M28256@PLCC32 [DX2032]
M28C010 [DX0001]
M28C010@TSOP32 [DX1002]
M28C010R@PLCC32 [DX2032]
M28C010W [DX0001]
M28C010W@TSOP32 [DX1002]
M28C17@SOIC28 [DX1033]

M28C64 [DX0001]
M28C64@PLCC32 [DX2032]
M28C64@TSOP28 [DX1024]
M28C64C [DX0001]
M28C64C@PLCC32 [DX2032]
M28C64C@SOIC28 [DX1033]
M28C64C@TSOP28 [DX1024]
M28C64X [DX0001]
M28C64X@PLCC32 [DX2032]
M28C64X@TSOP28 [DX1024]
M28F101 [DX0001]
M28F101(REVERSE)@TSOP32 [DX1002]
M28F101@PLCC32 [DX2032]
M28F101@TSOP32 [DX1002]
M28F102 [DX0001]
M28F102@PLCC44 [DX2044]
M28F102@TSOP40 [DX1005]
M28F151 [DX0001]
M28F151(REVERSE)@TSOP32 [DX1002]
M28F151@PLCC32 [DX2032]
M28F151@TSOP32 [DX1002]
M28F201 [DX0001]
M28F201(REVERSE)@TSOP32 [DX1002]
M28F201@PLCC32 [DX2032]
M28F201@TSOP32 [DX1002]
M28F210@PSOP44 [DX1014]
M28F210@TSOP48 [DX1004]
M28F211@TSOP40 [DX1006]
M28F220@PSOP44 [DX1014]
M28F220@TSOP48 [DX1004]
M28F221@TSOP40 [DX1006]
M28F256 [DX0001]
M28F256(REVERSE)@TSOP32 [DX1002]
M28F256@PLCC32 [DX2032]
M28F256@TSOP32 [DX1002]
M28F411@TSOP40 [DX1006]
M28F421@TSOP40 [DX1006]
M28F512 [DX0001]
M28F512(REVERSE)@TSOP32 [DX1002]
M28F512@PLCC32 [DX2032]
M28F512@TSOP32 [DX1002]
M28LV64 [DX0001]
M28LV64@PLCC32 [DX2032]
M28LV64@TSOP28 [DX1024]
M28R400CB@FBGA48 [DX5031]
M28R400CT@FBGA48 [DX5031]
M28V411@TSOP40 [DX1006]
M28V421@TSOP40 [DX1006]
M28W160B@FBGA48 [DX5031]
M28W160B@TSOP48 [DX1004]
M28W160BB@FBGA48 [DX5031]
M28W160BB@TSOP48 [DX1004]
M28W160BT@FBGA48 [DX5031]
M28W160BT@TSOP48 [DX1004]
M28W160CB@FBGA48 [DX5031]
M28W160CB@TSOP48 [DX1004]
M28W160CT@FBGA48 [DX5031]
M28W160CT@TSOP48 [DX1004]
M28W160ECB@FBGA48 [DX5031]
M28W160ECB@TSOP48 [DX1004]
M28W160ECT@FBGA48 [DX5031]
M28W160ECT@TSOP48 [DX1004]
M28W160ESB@FBGA64 [DX5004]
M28W160EST@FBGA64 [DX5004]
M28W160FSB@FBGA46 [DX5031]
M28W160FSB@FBGA64 [DX5004]
M28W160FST@FBGA46 [DX5031]
M28W160FST@FBGA64 [DX5004]
M28W160T@FBGA48 [DX5031]
M28W160T@TSOP48 [DX1004]
M28W320CB@FBGA48 [DX5031]
M28W320CB@TSOP48 [DX1004]
M28W320CT@FBGA48 [DX5031]
M28W320CT@TSOP48 [DX1004]
M28W320ECB@FBGA48 [DX5031]
M28W320ECB@TSOP48 [DX1004]
M28W320ECT@FBGA48 [DX5031]
M28W320ECT@TSOP48 [DX1004]
M28W320FCB@FBGA48 [DX5031]
M28W320FCB@TSOP48 [DX1004]
M28W320FCT@FBGA48 [DX5031]
M28W320FCT@TSOP48 [DX1004]
M28W320FSB@FBGA47 [DX5031]
M28W320FSB@FBGA64 [DX5004]
M28W320FST@FBGA47 [DX5031]
M28W320FST@FBGA64 [DX5004]
M28W320FSU(Double)@FBGA64 [DX5004]
M28W320FSU@FBGA47 [DX5031]
M28W320FSU@FBGA64 [DX5004]
M28W320HSB@FBGA47 [DX5031]
M28W320HSB@FBGA64 [DX5004]
M28W320HST@FBGA47 [DX5031]
M28W320HST@FBGA64 [DX5004]
M28W320HSU(Double)@FBGA64 [DX5004]

M28W320HSU@FBGA64 [DX5004]
M28W640CB@TSOP48 [DX1004]
M28W640CT@TSOP48 [DX1004]
M28W640ECB@TSOP48 [DX1004]
M28W640ECT@TSOP48 [DX1004]
M28W640FCB@TSOP48 [DX1004]
M28W640FCT@TSOP48 [DX1004]
M28W640FST@FBGA64 [DX5004]
M28W640HCB@FBGA48 [DX5078]
M28W640HCT@FBGA48 [DX5078]
M28W640HSB@FBGA48 [DX5031]
M28W640HST@FBGA48 [DX5031]
M28W640HSU@FBGA48 [DX5031]
M28W800B@FBGA48 [DX5031]
M28W800BB@FBGA48 [DX5031]
M28W800BT@FBGA48 [DX5031]
M28W800CB@FBGA48 [DX5031]
M28W800CT@FBGA48 [DX5031]
M28W800T@FBGA48 [DX5031]
M29DW127G@FBGA64 [DX5004]
M29DW128F(Mirror)@FBGA64 [DX5004]
M29DW128F(Mirror)@TSOP56 [DX1011]
M29DW128F(Q_Word)@FBGA64 [DX5004]
M29DW128F(Q_Word)@TSOP56 [DX1011]
M29DW128G@FBGA64 [DX5004]
M29DW256G@LFBGA64 [DX5074]
M29DW256G@TSOP56 [DX1055]
M29DW323DB@TFBGA63 [DX5047]
M29DW323DT@TFBGA48 [DX5002]
M29DW323DT@TSOP48 [DX1004]
M29DW324DB@TFBGA63 [DX5047]
M29DW324DT@TFBGA48 [DX5002]
M29DW324DT@TSOP48 [DX1004]
M29DW640D@TSOP48 [DX1004]
M29DW640F@TSOP48 [DX1004]
M29DW641F@TSOP48 [DX1004]
M29F002B@PLCC32 [DX2032]
M29F002BB [DX0001]
M29F002BB@TSOP32 [DX1002]
M29F002BNT@PLCC32 [DX2032]
M29F002BT [DX0001]
M29F002BT@TSOP32 [DX1002]
M29F002T@PLCC32 [DX2032]
M29F010B [DX0001]
M29F010B@TSOP32 [DX1002]
M29F016B@TSOP40 [DX1006]
M29F016D@TSOP40 [DX1006]
M29F040 [DX0001]
M28W640CB@FBGA48 [DX5078]
M28W640CT@FBGA48 [DX5078]
M28W640ECB@FBGA48 [DX5078]
M28W640ECT@FBGA48 [DX5078]
M28W640FCB@FBGA48 [DX5078]
M28W640FCT@FBGA48 [DX5078]
M28W640FSB@FBGA64 [DX5004]
M28W640FSU@FBGA64 [DX5004]
M28W640HCB@TSOP48 [DX1004]
M28W640HCT@TSOP48 [DX1004]
M28W640HSB@FBGA64 [DX5004]
M28W640HST@FBGA64 [DX5004]
M28W640HSU@FBGA64 [DX5004]
M28W800B@TSOP48 [DX1004]
M28W800BB@TSOP48 [DX1004]
M28W800BT@TSOP48 [DX1004]
M28W800CB@TSOP48 [DX1004]
M28W800CT@TSOP48 [DX1004]
M28W800T@TSOP48 [DX1004]
M29DW127G@TSOP56 [DX1011]
M29DW128G@TSOP56 [DX1055]
M29DW256G@TFBGA64 [DX5004]
M29DW323DB@TFBGA48 [DX5002]
M29DW323DB@TSOP48 [DX1004]
M29DW323DT@TFBGA63 [DX5047]
M29DW324DB@TFBGA48 [DX5002]
M29DW324DB@TSOP48 [DX1004]
M29DW324DT@TFBGA63 [DX5047]
M29DW640D@FBGA63 [DX5047]
M29DW640F@FBGA48 [DX5002]
M29DW641F@FBGA48 [DX5002]
M29F002B [DX0001]
M29F002B@TSOP32 [DX1002]
M29F002BB@PLCC32 [DX2032]
M29F002BNT [DX0001]
M29F002BNT@TSOP32 [DX1002]
M29F002BT@PLCC32 [DX2032]
M29F002T [DX0001]
M29F002T@TSOP32 [DX1002]
M29F010B@PLCC32 [DX2032]
M29F016B@PSOP44 [DX1014]
M29F016D@PSOP44 [DX1014]
M29F032D@TSOP40 [DX1006]
M29F040@PLCC32 [DX2032]

M29F040@TSOP32 [DX1002]
M29F040B [DX0001]
M29F040B@PLCC32 [DX2032]
M29F040B@TSOP32 [DX1002]
M29F080A@PSOP44 [DX1014]
M29F080A@TSOP40 [DX1006]
M29F080D@PSOP44 [DX1014]
M29F080D@TSOP40 [DX1006]
M29F100B@PSOP44 [DX1014]
M29F100B@TSOP48 [DX1004]
M29F100T@PSOP44 [DX1014]
M29F100T@TSOP48 [DX1004]
M29F102B@PLCC44 [DX2044]
M29F102B@TSOP40 [DX1005]
M29F102BB@PLCC44 [DX2044]
M29F102BB@TSOP40 [DX1005]
M29F160BB@TSOP48 [DX1004]
M29F160BT@TSOP48 [DX1004]
M29F160FB@FBGA48 [DX5002]
M29F160FB@TSOP48 [DX1043]
M29F160FT@FBGA48 [DX5002]
M29F160FT@TSOP48 [DX1043]
M29F200B@PSOP44 [DX1014]
M29F200B@TSOP48 [DX1004]
M29F200BB@PSOP44 [DX1014]
M29F200BB@TSOP48 [DX1004]
M29F200BT@PSOP44 [DX1014]
M29F200BT@TSOP48 [DX1004]
M29F200FB@FBGA48 [DX5002]
M29F200FB@PSOP44 [DX1014]
M29F200FB@TSOP48 [DX1043]
M29F200FT@FBGA48 [DX5002]
M29F200FT@PSOP44 [DX1014]
M29F200FT@TSOP48 [DX1043]
M29F200T@PSOP44 [DX1014]
M29F200T@TSOP48 [DX1004]
M29F320MT@TSOP48 [DX0001]
M29F400B@PSOP44 [DX1014]
M29F400B@TSOP48 [DX1004]
M29F400BB@PSOP44 [DX1014]
M29F400BB@TSOP48 [DX1004]
M29F400BT@PSOP44 [DX1014]
M29F400BT@TSOP48 [DX1004]
M29F400FB@FBGA48 [DX5002]
M29F400FB@PSOP44 [DX1014]
M29F400FB@TSOP48 [DX1043]
M29F400FT@FBGA48 [DX5002]
M29F400FT@PSOP44 [DX1014]
M29F400FT@TSOP48 [DX1043]
M29F400T@PSOP44 [DX1014]
M29F400T@TSOP48 [DX1004]
M29F512B@PLCC32 [DX2032]
M29F512B@TSOP32 [DX1003]
M29F640MT@TSOP48 [DX1043]
M29F800AB@PSOP44 [DX1014]
M29F800AB@TSOP48 [DX1004]
M29F800AT@PSOP44 [DX1014]
M29F800AT@TSOP48 [DX1004]
M29F800DB@PSOP44 [DX1014]
M29F800DB@TSOP48 [DX1004]
M29F800DT@PSOP44 [DX1014]
M29F800DT@TSOP48 [DX1004]
M29F800FB@FBGA48 [DX5002]
M29F800FB@PSOP44 [DX1014]
M29F800FB@TSOP48 [DX1043]
M29F800FT@FBGA48 [DX5002]
M29F800FT@PSOP44 [DX1014]
M29F800FT@TSOP48 [DX1043]
M29KW016E@PSOP44 [DX1014]
M29KW016E@TFBGA48 [DX5002]
M29KW016E@TSOP48 [DX1004]
M29KW032E@TFBGA48 [DX5002]
M29KW032E@TSOP48 [DX1004]
M29KW064E@TFBGA48 [DX5002]
M29KW064E@TSOP48 [DX1004]
M29PW032@BGA48 [DX5157]
M29PW032@PSOP44 [DX0001]
M29PW032@TSOP48 [DX0001]
M29S128LP@FBGA88 [DX5005]
M29S256LP@FBGA88 [DX5005]
M29V040@PLCC32 [DX2032]
M29V040@TSOP32 [DX1002]
M29W004B@TSOP40 [DX1006]
M29W004BB@TSOP40 [DX1006]
M29W004BT@TSOP40 [DX1006]
M29W004T@TSOP40 [DX1006]
M29W008AB@TSOP40 [DX1006]
M29W008AT@TSOP40 [DX1006]
M29W008B@TSOP40 [DX1006]
M29W008T@TSOP40 [DX1006]
M29W010B@PLCC32 [DX2032]
M29W010B@TSOP32 [DX1002]
M29W017D@FBGA48 [DX5022]
M29W017D@TSOP40 [DX1006]
M29W022BB [DX0001]
M29W022BB@PLCC32 [DX2032]

M29W022BB@TSOP32 [DX1002]
M29W022BT [DX0001]
M29W022BT@PLCC32 [DX2032]
M29W022BT@TSOP32 [DX1002]
M29W040@PLCC32 [DX2032]
M29W040@TSOP32 [DX1002]
M29W040B@PLCC32 [DX2032]
M29W040B@TSOP32 [DX1002]
M29W064FB@FBGA48 [DX5002]
M29W064FB@TSOP48 [DX1004]
M29W064FT@FBGA48 [DX5002]
M29W064FT@TSOP48 [DX1004]
M29W102BB@TSOP40 [DX1005]
M29W102BT@TSOP40 [DX1005]
M29W116BB@TSOP40 [DX1006]
M29W116BT@TSOP40 [DX1006]
M29W128FH(Mirror)@FBGA64 [DX5004]
M29W128FH(Mirror)@TSOP56 [DX1011]
M29W128FH(Q_Word)@FBGA64 [DX5004]
M29W128FH(Q_Word)@TSOP56 [DX1011]
M29W128FL(Mirror)@FBGA64 [DX5004]
M29W128FL(Mirror)@TSOP56 [DX1011]
M29W128FL(Q_Word)@FBGA64 [DX5004]
M29W128FL(Q_Word)@TSOP56 [DX1011]
M29W128GH(SD)@TSOP56 [DX1011]
M29W128GH@FBGA64 [DX5004]
M29W128GH@TSOP56 [DX1011]
M29W128GL@FBGA64 [DX5004]
M29W128GL@TSOP56 [DX1011]
M29W128GSH@FBGA64 [DX5004]
M29W128GSH@FBGA64(ZS) [DX5074]
M29W128GSH@TSOP56 [DX1055]
M29W128GSL@FBGA64 [DX5004]
M29W128GSL@FBGA64(ZS) [DX5074]
M29W128GSL@TSOP56 [DX1055]
M29W160BB@LBGA48 [DX5022]
M29W160BB@PSOP44 [DX1014]
M29W160BB@TSOP48 [DX1004]
M29W160BT@LBGA48 [DX5022]
M29W160BT@PSOP44 [DX1014]
M29W160BT@TSOP48 [DX1004]
M29W160DB@LBGA48 [DX5022]
M29W160DB@PSOP44 [DX1014]
M29W160DB@TSOP48 [DX1004]
M29W160DT@LBGA48 [DX5022]
M29W160DT@PSOP44 [DX1014]
M29W160DT@TSOP48 [DX1004]
M29W160EB(8bit)@TSOP48 [DX1004]
M29W160EB@LBGA48 [DX5002]
M29W160EB@LBGA64 [DX5074]
M29W160EB@PSOP44 [DX1014]
M29W160EB@TSOP48 [DX1004]
M29W160ET@LBGA48 [DX5002]
M29W160ET@LBGA64 [DX5074]
M29W160ET@PSOP44 [DX1014]
M29W160ET@TSOP48 [DX1004]
M29W160FB@LBGA48 [DX5002]
M29W160FB@TSOP48 [DX1004]
M29W160FT@LBGA48 [DX5002]
M29W160FT@TSOP48 [DX1004]
M29W200BB@PSOP44 [DX1014]
M29W200BB@TSOP48 [DX1004]
M29W200BT@PSOP44 [DX1014]
M29W200BT@TSOP48 [DX1004]
M29W256AD@FBGA48 [DX0001]
M29W256AD@FBGA88 [DX5005]
M29W256ADP@FBGA44 [DX5056]
M29W256ADP@FBGA88 [DX5005]
M29W256AP@FBGA88 [DX5005]
M29W256G2G@TSOP56 [DX0051]
M29W256GH@LFBGA64 [DX5074]
M29W256GH@TFBGA64 [DX5004]
M29W256GH@TSOP56 [DX1055]
M29W256GL@LFBGA64 [DX5074]
M29W256GL@TFBGA64 [DX5004]
M29W256GL@TSOP56 [DX1055]
M29W256GZD1@TSOP56 [DX0051]
M29W256JD@FBGA64 [DX5004]
M29W256JD@TSOP56 [DX1011]
M29W256JKT1@TSOP56 [DX0051]
M29W256JP@FBGA64 [DX5004]
M29W256JP@TSOP56 [DX1011]
M29W256LP@FBGA48 [DX0001]
M29W256LP@FBGA56 [DX5056]
M29W256LP@FBGA88 [DX5005]
M29W256MCD@FBGA107 [DX5005]
M29W256MCP@FBGA107 [DX5005]
M29W256MDD@FBGA105 [DX5005]

M29W256MDP@FBGA105 [DX5005]
M29W256PD@FBGA64 [DX5004]
M29W256PD@TSOP56 [DX1011]
M29W256PP@FBGA64 [DX5004]
M29W256PP@TSOP56 [DX1011]
M29W256TD@FBGA48 [DX5005]
M29W256TD@FBGA64 [DX5004]
M29W256TD@TSOP48 [DX1004]
M29W256TD@TSOP56 [DX1011]
M29W256TP@FBGA64 [DX5004]
M29W256TP@TSOP48 [DX1004]
M29W256TP@TSOP56 [DX1011]
M29W320DB@FBGA48 [DX5002]
M29W320DB@FBGA63 [DX5047]
M29W320DB@TSOP48 [DX1004]
M29W320DT@FBGA48 [DX5002]
M29W320DT@FBGA63 [DX5047]
M29W320DT@TSOP48 [DX1004]
M29W320EB@FBGA48 [DX5002]
M29W320EB@FBGA64 [DX5074]
M29W320EB@TSOP48 [DX1004]
M29W320ET@FBGA48 [DX5002]
M29W320ET@FBGA64 [DX5074]
M29W320ET@TSOP48 [DX1004]
M29W320FB@TSOP48 [DX1004]
M29W320FT@TSOP48 [DX1004]
M29W400B@PSOP44 [DX1014]
M29W400B@TSOP48 [DX1004]
M29W400BB@LBGA48 [DX5002]
M29W400BB@PSOP44 [DX1014]
M29W400BB@TSOP48 [DX1004]
M29W400BT@LBGA48 [DX5002]
M29W400BT@PSOP44 [DX1014]
M29W400BT@TSOP48 [DX1004]
M29W400DB(ZA)@LBGA48 [DX5039]
M29W400DB(ZE)@LBGA48 [DX5002]
M29W400DB@PSOP44 [DX1014]
M29W400DB@TSOP48 [DX1004]
M29W400DT(ZA)@LBGA48 [DX5039]
M29W400DT(ZE)@LBGA48 [DX5002]
M29W400DT@PSOP44 [DX1014]
M29W400DT@TSOP48 [DX1004]
M29W400T@PSOP44 [DX1014]
M29W400T@TSOP48 [DX1004]
M29W512B@PLCC32 [DX2032]
M29W512B@TSOP32 [DX1003]
M29W512G2G@TSOP56 [DX0051]
M29W512GH@TSOP56 [DX1055]
M29W512JKT@TSOP56 [DX0051]
M29W512TD@FBGA48 [DX5005]
M29W512TD@FBGA64 [DX5004]
M29W512TD@TSOP48 [DX0001]
M29W512TD@TSOP56 [DX1011]
M29W640DB@FBGA63 [DX5047]
M29W640DB@TSOP48 [DX1004]
M29W640DT@FBGA63 [DX5047]
M29W640DT@TSOP48 [DX1004]
M29W640FB(Q_Word)@FBGA48 [DX5002]
M29W640FB(Q_Word)@TSOP48 [DX1004]
M29W640FB@FBGA48 [DX5002]
M29W640FB@TSOP48 [DX1004]
M29W640FT(Q_Word)@FBGA48 [DX5002]
M29W640FT(Q_Word)@TSOP48 [DX1004]
M29W640FT@FBGA48 [DX5002]
M29W640FT@TSOP48 [DX1004]
M29W640GB(Mirror)@FBGA48 [DX5002]
M29W640GB(Mirror)@FBGA64 [DX5004]
M29W640GB(Mirror)@TSOP48 [DX1004]
M29W640GB(Mirror)@TSOP56 [DX1011]
M29W640GB(Q_Word)@FBGA48 [DX5002]
M29W640GB(Q_Word)@FBGA64 [DX5004]
M29W640GB(Q_Word)@TSOP48 [DX1004]
M29W640GB(Q_Word)@TSOP56 [DX1011]
M29W640GH(Mirror)@FBGA48 [DX5002]
M29W640GH(Mirror)@FBGA64 [DX5004]
M29W640GH(Mirror)@TSOP48 [DX1004]
M29W640GH(Mirror)@TSOP56 [DX1011]
M29W640GH(Q_Word)@FBGA48 [DX5002]

M29W640GH(Q_Word)@FBGA64 [DX5004]
M29W640GH(Q_Word)@TSOP48 [DX1004]
M29W640GH(Q_Word)@TSOP56 [DX1011]
M29W640GL(Mirror)@FBGA48 [DX5002]
M29W640GL(Mirror)@FBGA64 [DX5004]
M29W640GL(Mirror)@TSOP48 [DX1004]
M29W640GL(Mirror)@TSOP56 [DX1011]
M29W640GL(Q_Word)@FBGA48 [DX5002]
M29W640GL(Q_Word)@FBGA64 [DX5004]
M29W640GL(Q_Word)@TSOP48 [DX1004]
M29W640GL(Q_Word)@TSOP56 [DX1011]
M29W640GLH(Mirror)@FBGA48 [DX5002]
M29W640GLT(Mirror)@FBGA48 [DX5002]
M29W640GSB(Mirror)@FBGA48 [DX5002]
M29W640GSB(Mirror)@FBGA64 [DX5004]
M29W640GSB(Mirror)@TSOP48 [DX1004]
M29W640GSB(Mirror)@TSOP56 [DX1011]
M29W640GSB(Q_Word)@FBGA48 [DX5002]
M29W640GSB(Q_Word)@FBGA64 [DX5004]
M29W640GSB(Q_Word)@TSOP48 [DX1004]
M29W640GSB(Q_Word)@TSOP56 [DX1011]
M29W640GSH(Mirror)@FBGA48 [DX5002]
M29W640GSH(Mirror)@FBGA64 [DX5004]
M29W640GSH(Mirror)@TSOP48 [DX1004]
M29W640GSH(Mirror)@TSOP56 [DX1011]
M29W640GSH(Q_Word)@FBGA48 [DX5002]
M29W640GSH(Q_Word)@FBGA64 [DX5004]
M29W640GSH(Q_Word)@TSOP48 [DX1004]
M29W640GSH(Q_Word)@TSOP56 [DX1011]
M29W640GSL(Mirror)@FBGA64 [DX5004]
M29W640GSL(Mirror)@TSOP48 [DX1004]
M29W640GSL(Mirror)@TSOP56 [DX1011]
M29W640GSL(Q_Word)@FBGA48 [DX5002]
M29W640GSL(Q_Word)@FBGA64 [DX5004]
M29W640GSL(Q_Word)@TSOP48 [DX1004]
M29W640GSL(Q_Word)@TSOP56 [DX1011]
M29W640GST(Mirror)@FBGA64 [DX5004]
M29W640GST(Mirror)@TSOP48 [DX1004]
M29W640GST(Mirror)@TSOP56 [DX1011]
M29W640GST(Q_Word)@FBGA48 [DX5002]
M29W640GST(Q_Word)@FBGA64 [DX5004]
M29W640GST(Q_Word)@TSOP48 [DX1004]
M29W640GST(Q_Word)@TSOP56 [DX1011]
M29W640GT(Mirror)@FBGA48 [DX5002]
M29W640GT(Mirror)@FBGA64 [DX5004]
M29W640GT(Mirror)@TSOP48 [DX1004]
M29W640GT(Mirror)@TSOP56 [DX1011]
M29W640GT(Q_Word)@FBGA48 [DX5002]

M29W640GT(Q_Word)@FBGA64 [DX5004]
M29W640GT(Q_Word)@TSOP48 [DX1004]
M29W640GT(Q_Word)@TSOP56 [DX1011]
M29W641DH@TSOP48 [DX1004]
M29W641DL@TSOP48 [DX1004]
M29W641DU@FBGA63 [DX5047]
M29W800AB@LBGA48 [DX5039]
M29W800AB@PSOP44 [DX1014]
M29W800AB@TSOP48 [DX1004]
M29W800AT@LBGA48 [DX5039]
M29W800AT@PSOP44 [DX1014]
M29W800AT@TSOP48 [DX1004]
M29W800B@PSOP44 [DX1014]
M29W800B@TSOP48 [DX1004]
M29W800DB@FBGA48 [DX5002]
M29W800DB@PSOP44 [DX1014]
M29W800DB@TSOP48 [DX1004]
M29W800DT@FBGA48 [DX5002]
M29W800DT@PSOP44 [DX1014]
M29W800DT@TSOP48 [DX1004]
M29W800T@PSOP44 [DX1014]
M29W800T@TSOP48 [DX1004]
M30L0R7000B0@FBGA88 [DX5005]
M30L0R7000T0@FBGA88 [DX5005]
M30L0R8000B0@FBGA88 [DX5005]
M30L0R8000B2@FBGA88 [DX5005]
M30L0R8000T0@FBGA88 [DX5005]
M30L0R8000T2@FBGA88 [DX5005]
M30L0T8800B0@FBGA88 [DX5005]
M30L0T8800T0@FBGA88 [DX5005]
M30L0T8888B0@FBGA88 [DX5005]
M30L0T8888T0@FBGA88 [DX5005]
M30W0R6600B0@LFBGA88 [DX5005]
M30W0R6600D0@LFBGA88 [DX5005]
M30W0R6600T0@LFBGA88 [DX5005]
M30WR128B@LFBGA88 [DX5005]
M34C02 [DX0001]
M34C02@MSOP8 [DX4047]
M34C02@SOIC8 [DX1045]
M34C02@TSOP8 [DX1059]
M34D32 [DX0001]
M34D32@SOIC8 [DX1045]
M34D32@TSSOP8 [DX1059]
M34D64 [DX0001]
M34D64@SOIC8 [DX1045]
M34D64@TSSOP8 [DX1059]
M34E02 [DX0001]
M34E02@MSOP8 [DX1015]
M34E02@SOIC8 [DX1045]
M34E02@TSOP8 [DX1059]
M35080 [DX0001]
M35080@SOIC8 [DX1045]
M36A0W5020B0@FBGA66 [DX5026]
M36A0W5020T0@FBGA66 [DX5026]
M36A0W5030B0@FBGA66 [DX5026]
M36A0W5030T0@FBGA66 [DX5026]
M36A0W5040B0@FBGA66 [DX5026]
M36A0W5040B1@FBGA66 [DX5026]
M36A0W5040T0@FBGA66 [DX5026]
M36A0W5040T1@FBGA66 [DX5026]
M36C0W5030B0@FBGA56 [DX5045]
M36C0W5030T0@FBGA56 [DX5045]
M36C0W5040B0@FBGA56 [DX5045]
M36C0W5040T0@FBGA56 [DX5045]
M36C0W6040B0@FBGA56 [DX5045]
M36C0W6040T0@FBGA56 [DX5045]
M36C0W6050B0@FBGA56 [DX5045]
M36C0W6050T0@FBGA56 [DX5045]
M36D0R5030B0(EFP)@FBGA67 [DX5026]
M36D0R5030B0(Q_Word)@FBGA67 [DX5026]
M36D0R5030T0(EFP)@FBGA67 [DX5026]
M36D0R5030T0(Q_Word)@FBGA67 [DX5026]
M36D0R5040B0(EFP)@FBGA67 [DX5026]
M36D0R5040B0(Q_Word)@FBGA67 [DX5026]
M36D0R5040T0(EFP)@FBGA67 [DX5026]
M36D0R5040T0(Q_Word)@FBGA67 [DX5026]
M36D0R6040B0(EFP)@FBGA67 [DX5026]
M36D0R6040B0(Q_Word)@FBGA67 [DX5026]
M36D0R6040T0(EFP)@FBGA67 [DX5026]
M36D0R6040T0(Q_Word)@FBGA67 [DX5026]

M36DR232A@FBGA66 [DX5026]
M36DR232B@FBGA66 [DX5026]
M36DR432AD@FBGA66 [DX5026]
M36DR432BD@FBGA66 [DX5026]
M36L0R7040B0@FBGA88 [DX5005]
M36L0R7040T0@FBGA88 [DX5005]
M36L0R7050B0@FBGA88 [DX5005]
M36L0R7050B1@FBGA88 [DX5005]
M36L0R7050B2@FBGA88 [DX5005]
M36L0R7050B4@FBGA88 [DX5005]
M36L0R7050L1@FBGA88 [DX5005]
M36L0R7050L2@FBGA88 [DX5005]
M36L0R7050L3@FBGA56 [DX5099]
M36L0R7050L3@FBGA88 [DX5005]
M36L0R7050T0@FBGA88 [DX5005]
M36L0R7050T1@FBGA88 [DX5005]
M36L0R7050T2@FBGA88 [DX5005]
M36L0R7050T4@FBGA88 [DX5005]
M36L0R7050U1@FBGA88 [DX5005]
M36L0R7050U2@FBGA88 [DX5005]
M36L0R7050U3@FBGA56 [DX5099]
M36L0R7050U3@FBGA88 [DX5005]
M36L0R7060B1@FBGA88 [DX5005]
M36L0R7060B2@FBGA88 [DX5005]
M36L0R7060L1@FBGA88 [DX5005]
M36L0R7060L3@FBGA56 [DX5099]
M36L0R7060L3@FBGA88 [DX5005]
M36L0R7060T1@FBGA88 [DX5005]
M36L0R7060T2@FBGA88 [DX5005]
M36L0R7060U1@FBGA88 [DX5005]
M36L0R7060U3@FBGA56 [DX5099]
M36L0R7060U3@FBGA88 [DX5005]
M36L0R7070U3@FBGA133 [DX5069]
M36L0R8050L3@FBGA56 [DX5099]
M36L0R8050L3@FBGA88 [DX5005]
M36L0R8050U3@FBGA56 [DX5099]
M36L0R8050U3@FBGA88 [DX5005]
M36L0R8060B0@FBGA88 [DX5005]
M36L0R8060B1@FBGA88 [DX5005]
M36L0R8060B3@FBGA88 [DX5005]
M36L0R8060B5@FBGA88 [DX5005]
M36L0R8060B8@FBGA88 [DX5005]
M36L0R8060B9@FBGA88 [DX5005]
M36L0R8060L0@FBGA88 [DX5005]
M36L0R8060L3@FBGA56 [DX5099]
M36L0R8060L3@FBGA80 [DX5052]
M36L0R8060L3@FBGA88 [DX5005]
M36L0R8060T0@FBGA88 [DX5005]
M36L0R8060T1@FBGA88 [DX5005]
M36L0R8060T3@FBGA88 [DX5005]
M36L0R8060T5@FBGA88 [DX5005]
M36L0R8060T8@FBGA88 [DX5005]
M36L0R8060T9@FBGA88 [DX5005]
M36L0R8060U0@FBGA88 [DX5005]
M36L0R8060U3@FBGA56 [DX5099]
M36L0R8060U3@FBGA80 [DX5052]
M36L0R8060U3@FBGA88 [DX5005]
M36L0T7040B0@FBGA88 [DX5005]
M36L0T7040T0@FBGA88 [DX5005]
M36L0T7050B0@FBGA88 [DX5005]
M36L0T7050B1@FBGA88 [DX5005]
M36L0T7050B2@FBGA88 [DX5005]
M36L0T7050B3@FBGA88 [DX5005]
M36L0T7050T0@FBGA88 [DX5005]
M36L0T7050T1@FBGA88 [DX5005]
M36L0T7050T2@FBGA88 [DX5005]
M36L0T7050T3@FBGA88 [DX5005]
M36L0T7060B0@FBGA88 [DX5005]
M36L0T7060B1@FBGA88 [DX5005]
M36L0T7060B2@FBGA88 [DX5005]
M36L0T7060B3@FBGA88 [DX5005]
M36L0T7060T0@FBGA88 [DX5005]
M36L0T7060T1@FBGA88 [DX5005]
M36L0T7060T2@FBGA88 [DX5005]
M36L0T7060T3@FBGA88 [DX5005]
M36L0T8050B0@FBGA88 [DX5005]
M36L0T8050B1@FBGA88 [DX5005]
M36L0T8050B3@FBGA88 [DX5005]
M36L0T8050T0@FBGA88 [DX5005]
M36L0T8050T1@FBGA88 [DX5005]
M36L0T8050T3@FBGA88 [DX5005]
M36L0T8060B0@FBGA88 [DX5005]
M36L0T8060B1@FBGA88 [DX5005]
M36L0T8060B3@FBGA88 [DX5005]
M36L0T8060T0@FBGA88 [DX5005]
M36L0T8060T1@FBGA88 [DX5005]
M36L0T8060T3@FBGA88 [DX5005]
M36LLR7750B0@FBGA88 [DX5005]
M36LLR7750D0@FBGA88 [DX5005]
M36LLR7750T0@FBGA88 [DX5005]
M36LLR7760B0@FBGA88 [DX5005]
M36LLR7760D0@FBGA88 [DX5005]
M36LLR7760T0@FBGA88 [DX5005]
M36LLR8760B1@FBGA88 [DX5005]
M36LLR8760D1@FBGA88 [DX5005]
M36LLR8760M1@FBGA88 [DX5005]

M36LLR8760T1@FBGA88 [DX5005]
M36LLR8860B1@FBGA88 [DX5001]
M36LLR8860D1@FBGA88 [DX5001]
M36LLR8860M1@FBGA88 [DX5001]
M36LLR8860T1@FBGA88 [DX5001]
M36LLR8870B0@FBGA88 [DX5001]
M36LLR8870B1@FBGA88 [DX5001]
M36LLR8870D0@FBGA88 [DX5001]
M36LLR8870D1@FBGA88 [DX5001]
M36LLR8870M0@FBGA88 [DX5001]
M36LLR8870M1@FBGA88 [DX5001]
M36LLR8870T0@FBGA88 [DX5001]
M36LLR8870T1@FBGA88 [DX5001]
M36P0R8060E0ZAC@FBGA107 [DX5077]
M36P0R9020Z0EAD@FBGA88 [DX5005]
M36P0R9025Z0EAD@FBGA88 [DX5005]
M36P0R9040Z0EAD@FBGA88 [DX5005]
M36P0R9045Z0EAD@FBGA88 [DX5005]
M36P0R9060E0ZAC@FBGA107 [DX5077]
M36P0R9070E0ZAC@FBGA107 [DX5077]
M36P0R9070E1ZAC@FBGA107 [DX5077]
M36P0R9080Z0EAD@FBGA88 [DX5005]
M36P0R9084Z0EAD@FBGA88 [DX5005]
M36W0R5020B0(EFP)@FBGA88 [DX5005]
M36W0R5020B0(Q_Word)@FBGA88 [DX5005]
M36W0R5020T0(EFP)@FBGA88 [DX5005]
M36W0R5020T0(Q_Word)@FBGA88 [DX5005]
M36W0R5030B0(EFP)@FBGA88 [DX5005]
M36W0R5030B0(Q_Word)@FBGA88 [DX5005]
M36W0R5030T0(EFP)@FBGA88 [DX5005]
M36W0R5030T0(Q_Word)@FBGA88 [DX5005]
M36W0R5030U5@TFBGA52 [DX5127]
M36W0R5030U5@TFBGA88 [DX5005]
M36W0R5040B0(EFP)@FBGA88 [DX5005]
M36W0R5040B0(Q_Word)@FBGA88 [DX5005]
M36W0R5040B1(EFP)@FBGA88 [DX5005]
M36W0R5040B1(Q_Word)@FBGA88 [DX5005]
M36W0R5040B2(EFP)@FBGA88 [DX5005]
M36W0R5040B2(Q_Word)@FBGA88 [DX5005]
M36W0R5040B4(EFP)@FBGA88 [DX5005]
M36W0R5040B4(Q_Word)@FBGA88 [DX5005]
M36W0R5040B5(EFP)@FBGA88 [DX5005]
M36W0R5040B5(Q_Word)@FBGA88 [DX5005]
M36W0R5040B7(EFP)@FBGA88 [DX5005]
M36W0R5040B7(Q_Word)@FBGA88 [DX5005]
M36W0R5040L3@FBGA88 [DX5005]
M36W0R5040L4@TFBGA56 [DX5099]
M36W0R5040L4@TFBGA88 [DX5005]
M36W0R5040L6@TFBGA52 [DX5127]
M36W0R5040L6@TFBGA88 [DX5005]
M36W0R5040T0(EFP)@FBGA88 [DX5005]
M36W0R5040T0(Q_Word)@FBGA88 [DX5005]
M36W0R5040T1(EFP)@FBGA88 [DX5005]
M36W0R5040T1(Q_Word)@FBGA88 [DX5005]
M36W0R5040T2(EFP)@FBGA88 [DX5005]
M36W0R5040T2(Q_Word)@FBGA88 [DX5005]
M36W0R5040T4(EFP)@FBGA88 [DX5005]
M36W0R5040T4(Q_Word)@FBGA88 [DX5005]
M36W0R5040T5(EFP)@FBGA88 [DX5005]
M36W0R5040T5(Q_Word)@FBGA88 [DX5005]
M36W0R5040T7(EFP)@FBGA88 [DX5005]
M36W0R5040T7(Q_Word)@FBGA88 [DX5005]

M36W0R5040U3@FBGA88 [DX5005]
M36W0R5040U4@TFBGA56 [DX5099]
M36W0R5040U4@TFBGA88 [DX5005]
M36W0R5040U5@TFBGA52 [DX5127]
M36W0R5040U5@TFBGA88 [DX5005]
M36W0R5040U6@TFBGA52 [DX5127]
M36W0R5040U6@TFBGA88 [DX5005]
M36W0R5050L6@TFBGA52 [DX5127]
M36W0R5050L6@TFBGA88 [DX5005]
M36W0R5050U6@TFBGA52 [DX5127]
M36W0R5050U6@TFBGA88 [DX5005]
M36W0R6030B0(EFP)@FBGA88 [DX5005]
M36W0R6030B0(Q_Word)@FBGA88 [DX5005]
M36W0R6030T0(EFP)@FBGA88 [DX5005]
M36W0R6030T0(Q_Word)@FBGA88 [DX5005]
M36W0R6040B0(EFP)@FBGA88 [DX5005]
M36W0R6040B0(Q_Word)@FBGA88 [DX5005]
M36W0R6040B1(EFP)@FBGA88 [DX5005]
M36W0R6040B1(Q_Word)@FBGA88 [DX5005]
M36W0R6040B3(EFP)@FBGA88 [DX5005]
M36W0R6040B3(Q_Word)@FBGA88 [DX5005]
M36W0R6040B4(EFP)@FBGA88 [DX5005]
M36W0R6040B4(Q_Word)@FBGA88 [DX5005]
M36W0R6040B7(EFP)@FBGA88 [DX5005]
M36W0R6040B7(Q_Word)@FBGA88 [DX5005]
M36W0R6040L3@FBGA88 [DX5005]
M36W0R6040L4@TFBGA56 [DX5099]
M36W0R6040L4@TFBGA88 [DX5005]
M36W0R6040L6@TFBGA52 [DX5127]
M36W0R6040L6@TFBGA88 [DX5005]
M36W0R6040T0(EFP)@FBGA88 [DX5005]
M36W0R6040T0(Q_Word)@FBGA88 [DX5005]
M36W0R6040T1(EFP)@FBGA88 [DX5005]
M36W0R6040T1(Q_Word)@FBGA88 [DX5005]
M36W0R6040T3(EFP)@FBGA88 [DX5005]
M36W0R6040T3(Q_Word)@FBGA88 [DX5005]
M36W0R6040T4(EFP)@FBGA88 [DX5005]
M36W0R6040T4(Q_Word)@FBGA88 [DX5005]
M36W0R6040T7(EFP)@FBGA88 [DX5005]
M36W0R6040T7(Q_Word)@FBGA88 [DX5005]
M36W0R6040U3@FBGA88 [DX5005]
M36W0R6040U4@TFBGA56 [DX5099]
M36W0R6040U4@TFBGA88 [DX5005]
M36W0R6040U5@TFBGA52 [DX5127]
M36W0R6040U5@TFBGA88 [DX5005]
M36W0R6040U6@TFBGA52 [DX5127]
M36W0R6040U6@TFBGA88 [DX5005]
M36W0R6050B0(EFP)@FBGA88 [DX5005]
M36W0R6050B0(Q_Word)@FBGA88 [DX5005]
M36W0R6050B1(EFP)@FBGA88 [DX5005]
M36W0R6050B1(Q_Word)@FBGA88 [DX5005]
M36W0R6050B3(EFP)@FBGA88 [DX5005]
M36W0R6050B3(Q_Word)@FBGA88 [DX5005]
M36W0R6050B4(EFP)@FBGA88 [DX5005]
M36W0R6050B4(Q_Word)@FBGA88 [DX5005]
M36W0R6050L0@FBGA88 [DX5005]
M36W0R6050L4@TFBGA56 [DX5099]
M36W0R6050L4@TFBGA88 [DX5005]
M36W0R6050L6@TFBGA52 [DX5127]
M36W0R6050L6@TFBGA88 [DX5005]

M36W0R6050T0(EFP)@FBGA88 [DX5005]
M36W0R6050T0(Q_Word)@FBGA88 [DX5005]
M36W0R6050T1(EFP)@FBGA88 [DX5005]
M36W0R6050T1(Q_Word)@FBGA88 [DX5005]
M36W0R6050T3(EFP)@FBGA88 [DX5005]
M36W0R6050T3(Q_Word)@FBGA88 [DX5005]
M36W0R6050T4(EFP)@FBGA88 [DX5005]
M36W0R6050T4(Q_Word)@FBGA88 [DX5005]
M36W0R6050U0@FBGA88 [DX5005]
M36W0R6050U4@TFBGA88 [DX5005]
M36W0R6050U4@TFBGA56 [DX5099]
M36W0R6050U5@TFBGA88 [DX5005]
M36W0R6050U5@TFBGA56 [DX5099]
M36W0R6050U6@TFBGA88 [DX5005]
M36W0R6050U6@TFBGA52 [DX5127]
M36W0R7050B0(EFP)@FBGA88 [DX5005]
M36W0R7050B0(Q_Word)@FBGA88 [DX5005]
M36W0R7050T0(EFP)@FBGA88 [DX5005]
M36W0R7050T0(Q_Word)@FBGA88 [DX5005]
M36W0T5040B1(EFP)@FBGA88 [DX5005]
M36W0T5040B1(Q_Word)@FBGA88 [DX5005]
M36W0T5040T1(EFP)@FBGA88 [DX5005]
M36W0T5040T1(Q_Word)@FBGA88 [DX5005]
M36W0T6030B0(EFP)@FBGA88 [DX5005]
M36W0T6030B0(Q_Word)@FBGA88 [DX5005]
M36W0T6030T0(EFP)@FBGA88 [DX5005]
M36W0T6030T0(Q_Word)@FBGA88 [DX5005]
M36W0T6040B0(EFP)@FBGA88 [DX5005]
M36W0T6040B0(Q_Word)@FBGA88 [DX5005]
M36W0T6040B1(EFP)@FBGA88 [DX5005]
M36W0T6040B1(Q_Word)@FBGA88 [DX5005]
M36W0T6040B3(EFP)@FBGA88 [DX5005]
M36W0T6040B3(Q_Word)@FBGA88 [DX5005]
M36W0T6040T0(EFP)@FBGA88 [DX5005]
M36W0T6040T0(Q_Word)@FBGA88 [DX5005]
M36W0T6040T1(EFP)@FBGA88 [DX5005]
M36W0T6040T1(Q_Word)@FBGA88 [DX5005]
M36W0T6040T3(EFP)@FBGA88 [DX5005]
M36W0T6040T3(Q_Word)@FBGA88 [DX5005]
M36W0T6050B0(EFP)@FBGA88 [DX5005]
M36W0T6050B0(Q_Word)@FBGA88 [DX5005]
M36W0T6050B3(EFP)@FBGA88 [DX5005]
M36W0T6050B3(Q_Word)@FBGA88 [DX5005]
M36W0T6050T0(EFP)@FBGA88 [DX5005]
M36W0T6050T0(Q_Word)@FBGA88 [DX5005]
M36W0T6050T3(EFP)@FBGA88 [DX5005]
M36W0T6050T3(Q_Word)@FBGA88 [DX5005]
M36W0T7040B0(EFP)@FBGA88 [DX5005]
M36W0T7040B0(Q_Word)@FBGA88 [DX5005]
M36W0T7040T0(EFP)@FBGA88 [DX5005]
M36W0T7040T0(Q_Word)@FBGA88 [DX5005]

M36W0T7050B0(EFP)@FBGA88 [DX5005]
M36W0T7050B0(Q_Word)@FBGA88 [DX5005]
M36W0T7050T0(EFP)@FBGA88 [DX5005]
M36W0T7050T0(Q_Word)@FBGA88 [DX5005]
M36W216BI@LFBGA66 [DX5026]
M36W216TI@LFBGA66 [DX5026]
M36W416BG@LFBGA66 [DX5026]
M36W416TG@LFBGA66 [DX5026]
M36W432B@LFBGA66 [DX5026]
M36W432BG@LFBGA66 [DX5026]
M36W432T@FBGA66 [DX5026]
M36W432TG@LFBGA66 [DX5026]
M36W832BE@FBGA67 [DX5026]
M36W832TE@FBGA67 [DX5026]
M36W864BE@FBGA67 [DX5026]
M36W864TE@FBGA67 [DX5026]
M36WWR6650B0@LFBGA88 [DX5005]
M36WWR6650D0@LFBGA88 [DX5005]
M36WWR6650T0@LFBGA88 [DX5005]
M39L0R8090U3@FBGA133 [DX5069]
M39P0R9060E0ZAD@FBGA105 [DX5056]
M39P0R9070E0ZAD@FBGA105 [DX5056]
M39P0R9070E4ZAD@FBGA105 [DX5056]
M45PE10@SOIC8 [DX1045#4]
M45PE10@VQFPN8 [DX4005#4]
M45PE16@SOIC8 [DX1044#4]
M45PE16@VQFPN8 [DX4005#4]
M45PE20@SOIC8 [DX1045#4]
M45PE20@SOIC8(ISP) [DX0001]
M45PE20@VQFPN8 [DX4005#4]
M45PE20@VQFPN8(ISP) [DX0001]
M45PE40@SOIC8 [DX1044#4]
M45PE40@SOIC8(ISP) [DX0001]
M45PE40@VQFPN8 [DX4005#4]
M45PE40@VQFPN8(ISP) [DX0001]
M45PE80@SOIC16 [DX1033#4]
M45PE80@SOIC16(ISP) [DX0001]
M45PE80@SOIC8 [DX1044#4]
M45PE80@SOIC8(ISP) [DX0001]
M45PE80@VQFPN8 [DX4005#4]
M45PE80@VQFPN8(ISP) [DX0001]
M48C02 [DX0001]
M48C02B [DX0001]
M48C12 [DX0001]
M48C12B [DX0001]
M48T02 [DX0001]
M48T02B [DX0001]
M48T08 [DX0001]
M48T12 [DX0001]
M48T128V [DX0001]
M48T128Y [DX0001]
M48T129V [DX0001]
M48T129Y [DX0001]
M48T12B [DX0001]
M48T18 [DX0001]
M48T30 [DX0001]
M48T30Y [DX0001]
M48T32 [DX0001]
M48T32Y [DX0001]
M48T35 [DX0001]
M48T35@SOIC28 [DX1033]
M48T35AV [DX0001]
M48T35AV@SOIC28 [DX1033]
M48T35AY [DX0001]
M48T35AY@SOIC28 [DX1033]
M48T35Y [DX0001]
M48T35Y@SOIC28 [DX1033]
M48T512AV [DX0001]
M48T512AY [DX0001]
M48T512V [DX0001]
M48T512Y [DX0001]
M48T513V [DX0001]
M48T513Y [DX0001]
M48T559 [DX0001]
M48T559@SOIC28 [DX1035]
M48T559Y [DX0001]
M48T559Y@SOIC28 [DX1035]
M48T58 [DX0001]
M48T58@SOIC28 [DX1033]
M48T58Y [DX0001]
M48T58Y@SOIC28 [DX1033]
M48T59 [DX0001]
M48T59@SOIC28 [DX1033]
M48T59V [DX0001]
M48T59V@SOIC28 [DX1033]
M48T59Y [DX0001]
M48T59Y@SOIC28 [DX1033]
M48Z02 [DX0001]
M48Z02B [DX0001]
M48Z08 [DX0001]
M48Z12 [DX0001]
M48Z128 [DX0001]

M48Z128V [DX0001]
M48Z128Y [DX0001]
M48Z129V [DX0001]
M48Z129Y [DX0001]
M48Z12B [DX0001]
M48Z18 [DX0001]
M48Z30 [DX0001]
M48Z30Y [DX0001]
M48Z32 [DX0001]
M48Z32Y [DX0001]
M48Z35 [DX0001]
M48Z35@SOIC28 [DX1033]
M48Z35Y [DX0001]
M48Z35Y@SOIC28 [DX1033]
M48Z512AV [DX0001]
M48Z512AY [DX0001]
M48Z512V [DX0001]
M48Z512Y [DX0001]
M48Z513V [DX0001]
M48Z513Y [DX0001]
M48Z58 [DX0001]
M48Z58@SOIC28 [DX1033]
M48Z58Y [DX0001]
M48Z58Y@SOIC28 [DX1033]
M48Z59 [DX0001]
M48Z59@SOIC28 [DX1033]
M48Z59W [DX0001]
M48Z59W@SOIC28 [DX1033]
M48Z59Y [DX0001]
M48Z59Y@SOIC28 [DX1033]
M50FLW040A@PLCC32 [DX2032]
M50FLW040A@TSOP40 [DX1006]
M50FLW040A@VSOP32 [DX1003]
M50FLW040B@PLCC32 [DX2032]
M50FLW040B@TSOP40 [DX1006]
M50FLW040B@VSOP32 [DX1003]
M50FLW080A@PLCC32 [DX2032]
M50FLW080A@TSOP40 [DX1006]
M50FLW080A@VSOP32 [DX1003]
M50FLW080B@PLCC32 [DX2032]
M50FLW080B@TSOP40 [DX1006]
M50FLW080B@VSOP32 [DX1003]
M50FW002@PLCC32 [DX2032]
M50FW016@TSOP40 [DX1006]
M50FW020@PLCC32 [DX2032]
M50FW040@PLCC32 [DX2032]
M50FW040@TSOP40 [DX1006]
M50FW080@PLCC32 [DX2032]
M50FW080@TSOP40 [DX1006]
M50FW080@VSOP32 [DX1003]
M50LPW002@PLCC32 [DX2032]
M50LPW012@PLCC32 [DX2032]
M50LPW020@PLCC32 [DX2032]
M50LPW040@PLCC32 [DX2032]
M50LPW040@TSOP40 [DX1006]
M50LPW041@PLCC32 [DX2032]
M50LPW041@TSOP40 [DX1006]
M50LPW080@PLCC32 [DX2032]
M50LPW080@TSOP40 [DX1006]
M50LPW116@TSOP40 [DX1006]
M58BW016DB@PQFP80(Big endian) [DX3020]
M58BW016DB@PQFP80(Little endian) [DX3020]
M58BW016DT@PQFP80(Big endian) [DX3020]
M58BW016DT@PQFP80(Little endian) [DX3020]
M58BW16FBPQFP80 [DX3020]
M58BW16FTPQFP80 [DX3020]
M58BW32FBPQFP80 [DX3020]
M58BW32FTPQFP80 [DX3020]
M58LR128FB@VFBGA56 [DX5032]
M58LR128FT@VFBGA56 [DX5032]
M58LR128GB@VFBGA56 [DX5032]
M58LR128GL@FBGA44 [DX5068]
M58LR128GT@VFBGA56 [DX5032]
M58LR128GU@FBGA44 [DX5068]
M58LR128HB@VFBGA56 [DX5032]
M58LR128HT@VFBGA56 [DX5032]
M58LR128KB@FBGA56 [DX5032]
M58LR128KB@FBGA88 [DX5005]
M58LR128KT@FBGA56 [DX5032]
M58LR128KT@FBGA88 [DX5005]
M58LR256GL@FBGA44 [DX5068]
M58LR256GU@FBGA44 [DX5068]
M58LR256KB@FBGA79 [DX5164]
M58LR256KB@FBGA88 [DX5005]
M58LR256KT@FBGA79 [DX5164]
M58LR256KT@FBGA88 [DX5005]
M58LT128GB@FBGA56 [DX5032]
M58LT128GSB@FBGA64 [DX5004]
M58LT128GST@FBGA64 [DX5004]
M58LT128GT@FBGA56 [DX5032]
M58LT128HSB@FBGA64 [DX5004]
M58LT128HST@FBGA64 [DX5004]

M58LT128KSB@FBGA64 [DX5004]
M58LT128KST@FBGA64 [DX5004]
M58LT256GB@FBGA64 [DX5004]
M58LT256GT@FBGA64 [DX5004]
M58LT256JSB@FBGA64 [DX5004]
M58LT256JST@FBGA64 [DX5004]
M58LT256KSB@FBGA64 [DX5004]
M58LT256KST@FBGA64 [DX5004]
M58LW032A@FBGA64 [DX5004]
M58LW032A@TSOP56 [DX1011]
M58LW032C@FBGA64 [DX5004]
M58LW032C@TSOP56 [DX1011]
M58LW032D@FBGA64 [DX5004]
M58LW032D@TSOP56 [DX1011]
M58LW064C@FBGA64 [DX5004]
M58LW064C@TSOP56 [DX1011]
M58LW064D@FBGA64 [DX5004]
M58LW064D@TSOP56 [DX1011]
M58LW128A@FBGA64 [DX5004]
M58LW128A@TSOP56 [DX1011]
M58PR001LE@TFGBA105 [DX5056]
M58PR001LE@TFGBA107 [DX5077]
M58PR512LE@TFGBA105 [DX5056]
M58PR512LE@TFGBA107 [DX5077]
M58WR016KB(EFP)@FBGA56 [DX5032]
M58WR016KB(EFP)@FBGA88 [DX5005]
M58WR016KB(Q_Word)@FBGA56 [DX5032]
M58WR016KB(Q_Word)@FBGA88 [DX5005]
M58WR016KL@FBGA44 [DX5176]
M58WR016KT(EFP)@FBGA56 [DX5032]
M58WR016KT(EFP)@FBGA88 [DX5005]
M58WR016KT(Q_Word)@FBGA56 [DX5032]
M58WR016KT(Q_Word)@FBGA88 [DX5005]
M58WR016KU@FBGA44 [DX5176]
M58WR016QB(EFP)@FBGA56 [DX5032]
M58WR016QB(Q_Word)@FBGA56 [DX5032]
M58WR016QL@FBGA44 [DX5176]
M58WR016QT(EFP)@FBGA56 [DX5032]
M58WR016QT(Q_Word)@FBGA56 [DX5032]
M58WR016QU@FBGA44 [DX5176]
M58WR032EB(EFP)@FBGA56 [DX5032]
M58WR032EB(Q_Word)@FBGA56 [DX5032]
M58WR032ET(EFP)@FBGA56 [DX5032]
M58WR032ET(Q_Word)@FBGA56 [DX5032]
M58WR032FB(EFP)@FBGA56 [DX5032]
M58WR032FB(Q_Word)@FBGA56 [DX5032]
M58WR032FT(EFP)@FBGA56 [DX5032]
M58WR032FT(Q_Word)@FBGA56 [DX5032]
M58WR032HB(EFP)@FBGA56 [DX5032]
M58WR032HB(Q_Word)@FBGA56 [DX5032]
M58WR032HT(EFP)@FBGA56 [DX5032]
M58WR032HT(Q_Word)@FBGA56 [DX5032]
M58WR032KB(EFP)@FBGA56 [DX5032]
M58WR032KB(EFP)@FBGA88 [DX5005]
M58WR032KB(Q_Word)@FBGA56 [DX5032]
M58WR032KB(Q_Word)@FBGA88 [DX5005]
M58WR032KL@FBGA44 [DX5176]
M58WR032KT(EFP)@FBGA56 [DX5032]
M58WR032KT(EFP)@FBGA88 [DX5005]
M58WR032KT(Q_Word)@FBGA56 [DX5032]
M58WR032KT(Q_Word)@FBGA88 [DX5005]
M58WR032KU@FBGA44 [DX5176]
M58WR032QB(EFP)@FBGA56 [DX5032]
M58WR032QB(Q_Word)@FBGA56 [DX5032]
M58WR032QL@FBGA44 [DX5176]
M58WR032QT(EFP)@FBGA56 [DX5032]
M58WR032QT(Q_Word)@FBGA56 [DX5032]
M58WR032QU@FBGA44 [DX5176]
M58WR064EB(EFP)@FBGA56 [DX5032]
M58WR064EB(Q_Word)@FBGA56 [DX5032]

M58WR064ET(EFP)@FBGA56 [DX5032]
M58WR064ET(Q_Word)@FBGA56 [DX5032]
M58WR064FB(EFP)@FBGA56 [DX5032]
M58WR064FB(Q_Word)@FBGA56 [DX5032]
M58WR064FT(EFP)@FBGA56 [DX5032]
M58WR064FT(Q_Word)@FBGA56 [DX5032]
M58WR064HB(EFP)@FBGA56 [DX5032]
M58WR064HB(Q_Word)@FBGA56 [DX5032]
M58WR064HL@FBGA44 [DX5066]
M58WR064HT(EFP)@FBGA56 [DX5032]
M58WR064HT(Q_Word)@FBGA56 [DX5032]
M58WR064HU@FBGA44 [DX5066]
M58WR064KB(EFP)@FBGA56 [DX5032]
M58WR064KB(EFP)@FBGA88 [DX5005]
M58WR064KB(Q_Word)@FBGA56 [DX5032]
M58WR064KB(Q_Word)@FBGA88 [DX5005]
M58WR064KL@FBGA44 [DX5176]
M58WR064KT(EFP)@FBGA56 [DX5032]
M58WR064KT(EFP)@FBGA88 [DX5005]
M58WR064KT(Q_Word)@FBGA56 [DX5032]
M58WR064KT(Q_Word)@FBGA88 [DX5005]
M58WR064KU@FBGA44 [DX5176]
M58WR128FB(EFP)@FBGA56 [DX5032]
M58WR128FB(Q_Word)@FBGA56 [DX5032]
M58WR128FT(EFP)@FBGA56 [DX5032]
M58WR128FT(Q_Word)@FBGA56 [DX5032]
M58WT032KB(EFP)@FBGA88 [DX5005]
M58WT032KB(Q_Word)@FBGA88 [DX5005]
M58WT032KT(EFP)@FBGA88 [DX5005]
M58WT032KT(Q_Word)@FBGA88 [DX5005]
M58WT064KB(EFP)@FBGA88 [DX5005]
M58WT064KB(Q_Word)@FBGA88 [DX5005]
M58WT064KT(EFP)@FBGA88 [DX5005]
M58WT064KT(Q_Word)@FBGA88 [DX5005]
M59DR008E@FBGA48 [DX5060]
M59DR008E@TSOP48 [DX1004]
M59DR008F@FBGA48 [DX5060]
M59DR008F@TSOP48 [DX1004]
M59DR016C@FBGA48 [DX5060]
M59DR016D@FBGA48 [DX5060]
M59DR032A@FBGA48 [DX5060]
M59DR032A@TSOP48 [DX1004]
M59DR032B@FBGA48 [DX5060]
M59DR032B@TSOP48 [DX1004]
M59DR032EA@FBGA48 [DX5060]
M59DR032EB@FBGA48 [DX5060]
M59PW016 [DX0001]
M59PW016@PSOP44 [DX1014]
M59PW016@SDIP42 [DX0042]
M59PW016@TSOP48 [DX1004]
M59PW032@PSOP44 [DX1014]
M59PW032@TSOP48 [DX1004]
M59PW064@PSOP44 [DX1014]
M59PW1282@PSOP44 [DX1014]
M72DW64000B@FBGA73 [DX5001]
M72DW75000C@FBGA73 [DX5001]
M72DW75001C@FBGA73 [DX5001]
M72DW76001D@FBGA73 [DX5001]
M76DW52003BA@FBGA73 [DX5001]
M76DW52003TA@FBGA73 [DX5001]
M76DW52004BA@FBGA73 [DX5001]
M76DW52004TA@FBGA73 [DX5001]
M76DW62000A@FBGA73 [DX5001]
M76DW63000A@FBGA73 [DX5001]
M87C257 [DX0001]
M87C257@PLCC32 [DX2032]
M93C06(08bit) [DX0001]
M93C06(08bit)@SOIC8 [DX1045]
M93C06(16bit) [DX0001]
M93C06(16bit)@SOIC8 [DX1045]

M93C46(08bit) [DX0001]
M93C46(08bit)@MLP8 [DX4001]
M93C46(08bit)@MSOP8 [DX1015]
M93C46(08bit)@SOIC8 [DX1045]
M93C46(08bit)@TSSOP8 [DX1059]
M93C46(16bit) [DX0001]
M93C46(16bit)@MLP8 [DX4001]
M93C46(16bit)@MSOP8 [DX1015]
M93C46(16bit)@SOIC8 [DX1045]
M93C46(16bit)@TSSOP8 [DX1059]
M93C46R(08bit) [DX0001]
M93C46R(08bit)@MLP8 [DX4001]
M93C46R(08bit)@MSOP8 [DX1015]
M93C46R(08bit)@SOIC8 [DX1045]
M93C46R(08bit)@TSSOP8 [DX1059]
M93C46R(16bit) [DX0001]
M93C46R(16bit)@MLP8 [DX4001]
M93C46R(16bit)@MSOP8 [DX1015]
M93C46R(16bit)@SOIC8 [DX1045]
M93C46R(16bit)@TSSOP8 [DX1059]
M93C46W(08bit) [DX0001]
M93C46W(08bit)@MLP8 [DX4001]
M93C46W(08bit)@MSOP8 [DX1015]
M93C46W(08bit)@SOIC8 [DX1045]
M93C46W(08bit)@TSSOP8 [DX1059]
M93C46W(16bit) [DX0001]
M93C46W(16bit)@MLP8 [DX4001]
M93C46W(16bit)@MSOP8 [DX1015]
M93C46W(16bit)@SOIC8 [DX1045]
M93C46W(16bit)@TSSOP8 [DX1059]
M93C56(08bit) [DX0001]
M93C56(08bit)@MLP8 [DX4001]
M93C56(08bit)@MSOP8 [DX1015]
M93C56(08bit)@SOIC8 [DX1045]
M93C56(08bit)@TSSOP8 [DX1059]
M93C56(16bit) [DX0001]
M93C56(16bit)@MLP8 [DX4001]
M93C56(16bit)@MSOP8 [DX1015]
M93C56(16bit)@SOIC8 [DX1045]
M93C56(16bit)@TSSOP8 [DX1059]
M93C56R(08bit) [DX0001]
M93C56R(08bit)@MLP8 [DX4001]
M93C56R(08bit)@MSOP8 [DX1015]
M93C56R(08bit)@SOIC8 [DX1045]
M93C56R(08bit)@TSSOP8 [DX1059]
M93C56R(16bit) [DX0001]
M93C56R(16bit)@MLP8 [DX4001]
M93C56R(16bit)@MSOP8 [DX1015]
M93C56R(16bit)@SOIC8 [DX1045]
M93C56R(16bit)@TSSOP8 [DX1059]
M93C56W(08bit) [DX0001]
M93C56W(08bit)@MLP8 [DX4001]
M93C56W(08bit)@MSOP8 [DX1015]
M93C56W(08bit)@SOIC8 [DX1045]
M93C56W(08bit)@TSSOP8 [DX1059]
M93C56W(16bit) [DX0001]
M93C56W(16bit)@MLP8 [DX4001]
M93C56W(16bit)@MSOP8 [DX1015]
M93C56W(16bit)@SOIC8 [DX1045]
M93C56W(16bit)@TSSOP8 [DX1059]
M93C66(08bit) [DX0001]
M93C66(08bit)@MLP8 [DX4001]
M93C66(08bit)@MSOP8 [DX1015]
M93C66(08bit)@SOIC8 [DX1045]
M93C66(08bit)@TSSOP8 [DX1059]
M93C66(16bit) [DX0001]
M93C66(16bit)@MLP8 [DX4001]
M93C66(16bit)@MSOP8 [DX1015]
M93C66(16bit)@SOIC8 [DX1045]
M93C66(16bit)@TSSOP8 [DX1059]
M93C66R(08bit) [DX0001]
M93C66R(08bit)@MLP8 [DX4001]
M93C66R(08bit)@MSOP8 [DX1015]
M93C66R(08bit)@SOIC8 [DX1045]
M93C66R(08bit)@TSSOP8 [DX1059]
M93C66R(16bit) [DX0001]
M93C66R(16bit)@MLP8 [DX4001]
M93C66R(16bit)@MSOP8 [DX1015]
M93C66R(16bit)@SOIC8 [DX1045]
M93C66R(16bit)@TSSOP8 [DX1059]
M93C66W(08bit) [DX0001]
M93C66W(08bit)@MLP8 [DX4001]
M93C66W(08bit)@MSOP8 [DX1015]
M93C66W(08bit)@SOIC8 [DX1045]
M93C66W(08bit)@TSSOP8 [DX1059]
M93C66W(16bit) [DX0001]
M93C66W(16bit)@MLP8 [DX4001]
M93C66W(16bit)@MSOP8 [DX1015]
M93C66W(16bit)@SOIC8 [DX1045]
M93C66W(16bit)@TSSOP8 [DX1059]
M93C76(08bit) [DX0001]
M93C76(08bit)@MLP8 [DX4001]
M93C76(08bit)@MSOP8 [DX1015]
M93C76(08bit)@SOIC8 [DX1045]
M93C76(08bit)@TSSOP8 [DX1059]
M93C76(16bit) [DX0001]

M93C76(16bit)@MLP8 [DX4001]
M93C76(16bit)@SOIC8 [DX1045]
M93C76R(08bit) [DX0001]
M93C76R(08bit)@MSOP8 [DX1015]
M93C76R(08bit)@TSSOP8 [DX1059]
M93C76R(16bit)@MLP8 [DX4001]
M93C76R(16bit)@SOIC8 [DX1045]
M93C76W(08bit) [DX0001]
M93C76W(08bit)@MSOP8 [DX1015]
M93C76W(08bit)@TSSOP8 [DX1059]
M93C76W(16bit)@MLP8 [DX4001]
M93C76W(16bit)@SOIC8 [DX1045]
M93C86(08bit) [DX0001]
M93C86(08bit)@MSOP8 [DX1015]
M93C86(08bit)@TSSOP8 [DX1059]
M93C86(16bit)@MLP8 [DX4001]
M93C86(16bit)@SOIC8 [DX1045]
M93C86R(08bit) [DX0001]
M93C86R(08bit)@MSOP8 [DX1015]
M93C86R(08bit)@TSSOP8 [DX1059]
M93C86R(16bit)@MLP8 [DX4001]
M93C86R(16bit)@SOIC8 [DX1045]
M93C86W(08bit) [DX0001]
M93C86W(08bit)@MSOP8 [DX1015]
M93C86W(08bit)@TSSOP8 [DX1059]
M93C86W(16bit)@MLP8 [DX4001]
M93C86W(16bit)@SOIC8 [DX1045]
M93CS566 [DX0001]
M93S46 [DX0001]
M93S46@TSSOP8 [DX1059]
M93S46R@SOIC8 [DX1045]
M93S46W [DX0001]
M93S46W@TSSOP8 [DX1059]
M93S56@SOIC8 [DX1045]
M93S56R [DX0001]
M93S56R@TSSOP8 [DX1059]
M93S56W@SOIC8 [DX1045]
M93S66 [DX0001]
M93S66@TSSOP8 [DX1059]
M93S66R@SOIC8 [DX1045]
M93S66W [DX0001]
M93S66W@TSSOP8 [DX1059]
M95010(ISP) [DX0001]
M95010@SOIC8(ISP) [DX0001]
M95010@TSSOP8(ISP) [DX0001]
M95020(ISP) [DX0001]
M95020@SOIC8(ISP) [DX1016]
M95020@TSSOP8(ISP) [DX1059]
M93C76(16bit)@MSOP8 [DX1015]
M93C76(16bit)@TSSOP8 [DX1059]
M93C76R(08bit)@MLP8 [DX4001]
M93C76R(08bit)@SOIC8 [DX1045]
M93C76R(16bit) [DX0001]
M93C76R(16bit)@MSOP8 [DX1015]
M93C76R(16bit)@TSSOP8 [DX1059]
M93C76W(08bit)@MLP8 [DX4001]
M93C76W(08bit)@SOIC8 [DX1045]
M93C76W(16bit) [DX0001]
M93C76W(16bit)@MSOP8 [DX1015]
M93C76W(16bit)@TSSOP8 [DX1059]
M93C86(08bit)@MLP8 [DX4001]
M93C86(08bit)@SOIC8 [DX1045]
M93C86(16bit) [DX0001]
M93C86(16bit)@MSOP8 [DX1015]
M93C86(16bit)@TSSOP8 [DX1059]
M93C86R(08bit)@MLP8 [DX4001]
M93C86R(08bit)@SOIC8 [DX1045]
M93C86R(16bit) [DX0001]
M93C86R(16bit)@MSOP8 [DX1015]
M93C86R(16bit)@TSSOP8 [DX1059]
M93C86W(08bit)@MLP8 [DX4001]
M93C86W(08bit)@SOIC8 [DX1045]
M93C86W(16bit) [DX0001]
M93C86W(16bit)@MSOP8 [DX1015]
M93C86W(16bit)@TSSOP8 [DX1059]
M93CS566@SOIC8 [DX1045]
M93S46@SOIC8 [DX1045]
M93S46R [DX0001]
M93S46R@TSSOP8 [DX1059]
M93S46W@SOIC8 [DX1045]
M93S56 [DX0001]
M93S56@TSSOP8 [DX1059]
M93S56R@SOIC8 [DX1045]
M93S56W [DX0001]
M93S56W@TSSOP8 [DX1059]
M93S66@SOIC8 [DX1045]
M93S66R [DX0001]
M93S66R@TSSOP8 [DX1059]
M93S66W@SOIC8 [DX1045]
M95010 [DX0001]
M95010@SOIC8 [DX1045]
M95010@TSSOP8 [DX1059]
M95020 [DX0001]
M95020@SOIC8 [DX1045]
M95020@TSSOP8 [DX1059]
M95040 [DX0001]

M95040(ISP) [DX0001]
M95040@SOIC8(ISP) [DX1016]
M95040@TSSOP8(ISP) [DX1059]
M95080(ISP) [DX0001]
M95080@SOIC8(ISP) [DX0001]
M95080@TSSOP14(ISP) [DX0001]
M95080@TSSOP8(ISP) [DX0001]
M95128 [DX0001]
M95128@TSSOP14 [DX1000]
M95128@TSSOP8 [DX1059]
M95128@UFDFPN8 [DX4002]
M95128[150mil]@SOIC8(ISP)
M95128[200mil]@SOIC8(ISP)
M95160(ISP) [DX0001]
M95160@SOIC8(ISP) [DX0001]
M95160@TSSOP14(ISP) [DX0001]
M95160@TSSOP8(ISP) [DX0001]
M95256 [DX0001]
M95256@TSSOP14 [DX1000]
M95256@TSSOP8 [DX1059]
M95256@UFDFPN8 [DX4002]
M95256[150mil]@SOIC8(ISP)
M95256[200mil]@SOIC8(ISP)
M95320(ISP) [DX0001]
M95320@SOIC8(ISP) [DX0001]
M95320@TSSOP14(ISP) [DX0001]
M95320@TSSOP8(ISP) [DX0001]
M95512@SOIC8 [DX1045]
M95512@TSSOP8 [DX1059]
M95640 [DX0001]
M95640@SOIC8 [DX1045]
M95640@TSSOP14 [DX1000]
M95640@TSSOP8 [DX1059]
M95640@UFDFPN8 [DX4002]
M95M01-R@SOP8(150 mil) [DX1045#1]
M95M01-R@SOP8(200 mil) [DX1044#1]
M95M01-R@WLCS8 [DX0001]
M95M01-W@SOP8(150 mil) [DX1045#1]
M95M01-W@SOP8(200 mil) [DX1044#1]
M95M01-W@WLCS8 [DX0001]
M95M02-DR@SOP8(150 mil) [DX1045#1]
M95M02-DR@SOP8(200 mil) [DX1044#1]
M95M02-DR@WLCS8 [DX0001]
M95P02@SOIC8 [DX1045]
M95P04@SOIC8 [DX1045]
M95P08@SOIC8 [DX1045]
MC36P0R9025E0ZAD@FBGA88 [DX5005]
MC36P0R9045E0ZAD@FBGA88 [DX5005]
M95040@SOIC8 [DX1045]
M95040@TSSOP8 [DX1059]
M95080 [DX0001]
M95080@SOIC8 [DX1045]
M95080@TSSOP14 [DX1000]
M95080@TSSOP8 [DX1059]
M95080@UFDFPN8 [DX4002]
M95128(ISP)
M95128@TSSOP14(ISP)
M95128@TSSOP8(ISP)
M95128[150mil]@SOIC8 [DX1045]
M95128[200mil]@SOIC8 [DX1032]
M95160 [DX0001]
M95160@SOIC8 [DX1045]
M95160@TSSOP14 [DX1000]
M95160@TSSOP8 [DX1059]
M95160@UFDFPN8 [DX4002]
M95256(ISP)
M95256@TSSOP14(ISP)
M95256@TSSOP8(ISP)
M95256[150mil]@SOIC8 [DX1045]
M95256[200mil]@SOIC8 [DX1032]
M95320 [DX0001]
M95320@SOIC8 [DX1045]
M95320@TSSOP14 [DX1000]
M95320@TSSOP8 [DX1059]
M95320@UFDFPN8 [DX4002]
M95512@SOIC8(ISP)
M95512@TSSOP8(ISP)
M95640(ISP) [DX0001]
M95640@SOIC8(ISP) [DX0001]
M95640@TSSOP14(ISP) [DX0001]
M95640@TSSOP8(ISP) [DX0001]
M95P02 [DX0001]
M95P04 [DX0001]
M95P08 [DX0001]
MC36P0R9020E0ZAD@FBGA88 [DX5005]
MC36P0R9040E0ZAD@FBGA88 [DX5005]
MC36P0R9080E0ZAD@FBGA88 [DX5005]

MC36P0R9084E0ZAD@FBGA88 [DX5005]
MF38F5070M0Y1B@FBGA105 [DX5005]
MF38F5070M0Y3C@FBGA107 [DX5005]
MF48F5000M0U0BE [DX0001]
MF48F6000M0U0BE [DX0001]
MK48C02 [DX0001]
MK48C02B [DX0001]
MK48C12 [DX0001]
MK48C12B [DX0001]
MK48T02 [DX0001]
MK48T02B [DX0001]
MK48T08 [DX0001]
MK48T12 [DX0001]
MK48T12B [DX0001]
MK48T18 [DX0001]
MK48T32 [DX0001]
MK48T32Y [DX0001]
MK48T35 [DX0001]
MK48T35@SOIC28 [DX1033]
MK48T35Y [DX0001]
MK48T35Y@SOIC28 [DX1033]
MK48T512V [DX0001]
MK48T512Y [DX0001]
MK48Z02 [DX0001]
MK48Z02B [DX0001]
MK48Z08 [DX0001]
MK48Z12 [DX0001]
MK48Z12B [DX0001]
MK48Z18 [DX0001]
MK48Z32 [DX0001]
MK48Z32Y [DX0001]
MK48Z35 [DX0001]
MK48Z35@SOIC28 [DX1033]
MK48Z35Y [DX0001]
MK48Z35Y@SOIC28 [DX1033]
MK48Z512V [DX0001]
MK48Z512Y [DX0001]
MKI48Z02 [DX0001]
MKI48Z02B [DX0001]
MKI48Z12 [DX0001]
MKI48Z12B [DX0001]
MKI48Z18 [DX0001]
N29L064@FBGA48 [DX5157]
N29L064@PSOP44 [DX0001]
N29L064@TSOP48 [DX0001]
N29Q064@BGA48 [DX5157]
N29Q064@PSOP44 [DX0001]
N29Q064@TSOP48 [DX0001]
N5081H0HA1PB30H0@FBGA168 [DX5205]
N5081H0HA1PB30M0@FBGA168 [DX5205]
NAND01GR3B2BZA6@FBGA63 [DX5046]
NAND01GR3B2CZA6@FBGA63 [DX5046]
NAND01GW3A0AN6@TSOP48 [DX1004]
NAND01GW3B2AN6@TSOP48 [DX1004]
NAND01GW3B2BN6@TSOP48 [DX1004]
NAND01GW3B2BZA6@FBGA63 [DX5046]
NAND01GW3B2CN6@TSOP48 [DX1004-1]
NAND01GW3B2CZA6@FBGA63 [DX5046]
NAND01GW3M2AZC5E@FBGA137 [DX5011]
NAND01GW3M2BZB5@FBGA137 [DX5011]
NAND02GR3B2AZB6@FBGA63 [DX5044]
NAND02GR3B2CZA6@FBGA63 [DX5173]
NAND02GR3B2DZA6@FBGA63 [DX5046]
NAND02GW3B2AN6@TSOP48 [DX1004]
NAND02GW3B2CN6@TSOP48 [DX1004]
NAND02GW3B2CZA6@FBGA63 [DX5173]
NAND02GW3B2DN6@TSOP48 [DX1004]
NAND02GW3B2DZA6@FBGA63 [DX5046]
NAND04GW3B2BN6@TSOP48 [DX1004]
NAND04GW3B2DN6@TSOP48 [DX1004-1]
NAND04GW3C2BN6@TSOP48 [DX1004]
NAND08GW3B2AN6@TSOP48 [DX1004-3]
NAND08GW3B2CN6@TSOP48 [DX1004-3]
NAND08GW3F2AN6@TSOP48 [DX1004-1]
NAND128W3A0AN6@TSOP48 [DX1004]
NAND128W3A2BN6@TSOP48 [DX1004]
NAND16GW3C4AN1@TSOP48 [DX1004]
NAND256R3A2BZA6@VFBGA55 [DX5005]
NAND256R3A2BZA6E@VFBGA55 [DX5005]
NAND256W3A0AN6@TSOP48 [DX1004]
NAND256W3A2AV6@USOP48 [DX1042]
NAND256W3A2BN6@TSOP48 [DX1004]
NAND256W3A2BZA6@VFBGA55 [DX5005]
NAND512R3A2BZA6@TFBGA63 [DX5046]
NAND512R3A2CZA6@TFBGA63 [DX5046]
NAND512R3A2SZA6@FBGA63 [DX5046]
NAND512R3M0AZB5@FBGA107 [DX5028]
NAND512W3A0AN6@TSOP48 [DX1004]
NAND512W3A2BN6@TSOP48 [DX1004]
NAND512W3A2BZA6@TFBGA63 [DX5046]
NAND512W3A2CN6@TSOP48 [DX1004]

NAND512W3A2CZA6@TFBGA63 [DX5046]
NAND512W3A2DN6@TSOP48 [DX1004]
NAND512W3A2DZA6@FBGA63 [DX5046]
NAND512W3A2SN6@TSOP48 [DX1004]
NAND512W3A2SZA6@BGA63 [DX5046]
NAND88R3MOAZBB5@FBGA107 [DX5028]
NAND98R3MOAZBB5@FBGA107 [DX5028]
NAND98R3MOCZBB5@FBGA107 [DX5028]
NAND98R3M2AZBB5@FBGA107 [DX5028]
NAND99R3M4BZBB5@FBGA107 [DX5028]
NAND99R4M2AZBA5@FBGA149 [DX5013]
NANDA8R3NOAP4E5@FBGA152 [DX5137]
NANDA8R3N1AZBC5@FBGA137 [DX5011-1]
NANDA8R4N4AZBB5E@FBGA107 [DX5028]
NANDA9R3NOBZBB5@FBGA107 [DX5028]
NANDA9R3N1CZBC5@FBGA137 [DX5011-1]
NANDA9R3N2AZBB5@FBGA107 [DX5028]
NANDA9R3N4BZBB5@FBGA107 [DX5028]
NANDA9R4N2AZBA5@FBGA149 [DX5013]
NANDA9R4N4CZBA5@FBGA149 [DX5013]
NANDA9W3N6CZBB5@FBGA107 [DX5028]
NANDAAR4N4AZBA5@FBGA149 [DX5013]
NANDBAR4N2AZBA5@FBGA149 [DX5013]
NANDBAR4N5BZBC5@FBGA137 [DX5011]
NANDBBR4N9BZBC5@FBGA137 [DX5011]
NANDC9R4NOAZBA5@FBGA149 [DX5013]
NANDCBR4N5AZBC5@FBGA137 [DX5011]
NANDCBR4N5BZBC5@FBGA137 [DX5011]
NANDCBR4N9BZBC5@FBGA137 [DX5011]
NANDDBR4N5AZCC5@FBGA137 [DX5011]
ST24C01 [DX0001]
ST24C01@SOIC8 [DX1045]
ST24C02A [DX0001]
ST24C02A@SOIC8 [DX1045]
ST24C16 [DX0001]
ST24C16@SOIC8
ST24FC21 [DX0001]
ST24FC21@SOIC8 [DX1045]
ST24FW21 [DX0001]
ST24FW21@SOIC8 [DX1045]
ST24LC21B [DX0001]
ST24LC21B@SOIC8 [DX1045]
ST24LW21 [DX0001]
ST24LW21@SOIC8 [DX1045]
ST24W01 [DX0001]
ST24W01@SOIC8
ST24W02 [DX0001]
ST24W02@SOIC8
ST24W04C [DX0001]
ST24W04C@SOIC8
ST26C201 [DX0001]
ST26C201@PLCC32 [DX2032]
ST26C201@TSOP32 [DX1002]
ST27128A [DX0001]
ST27256 [DX0001]
ST2764A [DX0001]
ST27C256 [DX0001]
ST93C06(08bit) [DX0001]
ST93C06(08bit)@SOIC8 [DX1045]
ST93C06(16bit) [DX0001]
ST93C06(16bit)@SOIC8 [DX1045]
ST93C46(08bit) [DX0001]
ST93C46(08bit)@SOIC8 [DX1045]
ST93C46(16bit) [DX0001]
ST93C46(16bit)@SOIC8 [DX1045]
ST93C46A(08bit) [DX0001]
ST93C46A(08bit)@SOIC8 [DX1045]
ST93C46A(16bit) [DX0001]
ST93C46A(16bit)@SOIC8 [DX1045]
ST93C46C(08bit) [DX0001]
ST93C46C(08bit)@SOIC8 [DX1045]
ST93C46C(16bit) [DX0001]
ST93C46C(16bit)@SOIC8 [DX1045]
ST93C46T(08bit) [DX0001]
ST93C46T(08bit)@SOIC8 [DX1045]
ST93C46T(16bit) [DX0001]
ST93C46T(16bit)@SOIC8 [DX1045]
ST93C47C(08bit) [DX0001]
ST93C47C(08bit)@SOIC8 [DX1045]
ST93C47C(16bit) [DX0001]
ST93C47C(16bit)@SOIC8 [DX1045]
ST93C47T(08bit) [DX0001]
ST93C47T(08bit)@SOIC8 [DX1045]
ST93C47T(16bit) [DX0001]
ST93C47T(16bit)@SOIC8 [DX1045]
ST93C56(08bit) [DX0001]
ST93C56(08bit)@SOIC8 [DX1045]
ST93C56(16bit) [DX0001]
ST93C56(16bit)@SOIC8 [DX1045]
ST93C56B(08bit) [DX0001]
ST93C56B(08bit)@SOIC8 [DX1045]
ST93C56B(16bit) [DX0001]

ST93C56B(16bit)@SOIC8 [DX1045]
ST93C56C(08bit)@SOIC8 [DX1045]
ST93C56C(16bit)@SOIC8 [DX1045]
ST93C57C(08bit)@SOIC8 [DX1045]
ST93C57C(16bit)@SOIC8 [DX1045]
ST93C66(08bit)@SOIC8 [DX1045]
ST93C66(16bit)@SOIC8 [DX1045]
ST93C67(08bit)@SOIC8 [DX1045]
ST93C67(16bit)@SOIC8 [DX1045]
ST93C76(08bit)@SOIC8 [DX1045]
ST93C76(16bit)@SOIC8 [DX1045]
ST93C86(08bit)@SOIC8 [DX1045]
ST93C86(16bit)@SOIC8 [DX1045]
ST93CS46@SOIC8 [DX1045]
ST93CS47@SOIC8 [DX1045]
ST93CS56@SOIC8 [DX1045]
ST93CS566@SOIC8 [DX1045]
ST93CS57@SOIC8 [DX1045]
ST93CS66@SOIC14 [DX1016]
ST93CS67@SOIC14 [DX1016]
TS27C256 [DX0001]
TS27C64@PLCC32 [DX2032]
TS27C64A@PLCC32 [DX2032]
TS28C17A [DX0001]
ST93C56C(08bit) [DX0001]
ST93C56C(16bit) [DX0001]
ST93C57C(08bit) [DX0001]
ST93C57C(16bit) [DX0001]
ST93C66(08bit) [DX0001]
ST93C66(16bit) [DX0001]
ST93C67(08bit) [DX0001]
ST93C67(16bit) [DX0001]
ST93C76(08bit) [DX0001]
ST93C76(16bit) [DX0001]
ST93C86(08bit) [DX0001]
ST93C86(16bit) [DX0001]
ST93CS46 [DX0001]
ST93CS47 [DX0001]
ST93CS56 [DX0001]
ST93CS566 [DX0001]
ST93CS57 [DX0001]
ST93CS66 [DX0001]
ST93CS67 [DX0001]
STTS2002@TDFN8 [DX4002]
TS27C64 [DX0001]
TS27C64A [DX0001]
TS28C16A [DX0001]

MICROCONTROLLER

BlueNRG-MS@QFN32 [DX4015]
PSD211R@TQFP44 [DX3003]
PSD301@TQFP44 [DX3003]
PSD301L@PLCC44 [DX2044]
PSD301R@PLCC44 [DX2044]
PSD301RV@PLCC44 [DX2044]
PSD302@PLCC44 [DX2044]
PSD302B@PLCC44 [DX2044]
PSD302L@PLCC44 [DX2044]
PSD302R@PLCC44 [DX2044]
PSD302RV@PLCC44 [DX2044]
PSD303@PLCC44 [DX2044]
PSD303L@PLCC44 [DX2044]
PSD303R@PLCC44 [DX2044]
PSD303RV@PLCC44 [DX2044]
PSD311@PLCC44 [DX2044]
PSD311B@PLCC44 [DX2044]
PSD311L@TQFP44 [DX3003]
PSD311R@TQFP44 [DX3003]
PSD311V@PLCC44 [DX2044]
PSD211R@PLCC44 [DX2044]
PSD301@PLCC44 [DX2044]
PSD301B@PLCC44 [DX2044]
PSD301L@TQFP44 [DX3003]
PSD301R@TQFP44 [DX3003]
PSD301V@PLCC44 [DX2044]
PSD302@TQFP44 [DX3003]
PSD302B@PLCC44(USA) [DX2044]
PSD302L@TQFP44 [DX3003]
PSD302R@TQFP44 [DX3003]
PSD302V@PLCC44 [DX2044]
PSD303@TQFP44 [DX3003]
PSD303L@TQFP44 [DX3003]
PSD303R@TQFP44 [DX3003]
PSD303V@PLCC44 [DX2044]
PSD311@TQFP44 [DX3003]
PSD311L@PLCC44 [DX2044]
PSD311R@PLCC44 [DX2044]
PSD311RV@PLCC44 [DX2044]
PSD312@PLCC44 [DX2044]

PSD312@TQFP44 [DX3046]
PSD312B@PLCC44 [DX2044]
PSD312L@PLCC44 [DX2044]
PSD312L@TQFP44 [DX3046]
PSD312R@PLCC44 [DX2044]
PSD312R@TQFP44 [DX3046]
PSD312RV@PLCC44 [DX2044]
PSD312V@PLCC44 [DX2044]
PSD313@PLCC44 [DX2044]
PSD313@TQFP44 [DX3003]
PSD313-B@PLCC44 [DX2044]
PSD313-B@TQFP44 [DX3003]
PSD313L@PLCC44 [DX2044]
PSD313L@TQFP44 [DX3003]
PSD313R@PLCC44 [DX2044]
PSD313R@TQFP44 [DX3003]
PSD313RV@PLCC44 [DX2044]
PSD313V@PLCC44 [DX2044]
PSD813F1@PLCC52 [DX2052]
PSD813F1@QFP52 [DX3010]
PSD813F1@QFP52(*) [DX3010]
PSD813F1A@PLCC52 [DX2052]
PSD813F1V@PLCC52 [DX2052]
PSD813F1V@QFP52 [DX3010]
PSD813F1V@QFP52(*) [DX3010]
PSD813F1VA@PLCC52 [DX2052]
PSD813F2@PLCC52 [DX2052]
PSD813F2@TQFP52 [DX3010]
PSD813F2@TQFP52(*) [DX3010]
PSD813F2-15JIT [DX2052]
PSD813F2-15MIT [DX3010]
PSD813F2-15UIT [DX3044]
PSD813F2A@PLCC52 [DX2052]
PSD813F2A-15JIT [DX3044]
PSD813F2A-15MIT [DX3010]
PSD813F2A-15UIT [DX3044]
PSD813F2AV-15JIT [DX2052]
PSD813F2AV-15MIT [DX3010]
PSD813F2AV-15UIT [DX3044]
PSD813F2V@PLCC52 [DX2052]
PSD813F2V@TQFP52 [DX3010]
PSD813F2V@TQFP52(*) [DX3010]
PSD813F2V-15JIT [DX2052]
PSD813F2V-15MIT [DX3010]
PSD813F2V-15UIT [DX3044]
PSD813F2VA@PLCC52 [DX2052]
PSD813F4@PLCC52 [DX2052]
PSD813F4@TQFP52 [DX3010]
PSD813F4@TQFP52(*) [DX3010]
PSD813F4V@PLCC52 [DX2052]
PSD813F4V@TQFP52 [DX3010]
PSD813F4V@TQFP52(*) [DX3010]
PSD833F2@PLCC52 [DX2052]
PSD833F2@PQFP52 [DX3010]
PSD833F2@TQFP52(*) [DX3010]
PSD833F2V@PLCC52 [DX2052]
PSD833F2V@TQFP52 [DX3010]
PSD833F2V@TQFP52(*) [DX3010]
PSD834F2@PLCC52 [DX2052]
PSD834F2@PLCC52(new) [DX2052]
PSD834F2@TQFP52 [DX3009]
PSD834F2@TQFP52(new) [DX3009]
PSD834F2V@PLCC52 [DX2052]
PSD834F2V@PLCC52(new) [DX2052]
PSD834F2V@TQFP52 [DX3009]
PSD834F2V@TQFP52(new) [DX3009]
PSD853F2@PLCC52 [DX2052]
PSD853F2@PQFP52 [DX3010]
PSD853F2@TQFP52(*) [DX3010]
PSD853F2V@PLCC52 [DX2052]
PSD853F2V@TQFP52 [DX3010]
PSD853F2V@TQFP52(*) [DX3010]
PSD854F2@PLCC52 [DX2052]
PSD854F2@PLCC52(new) [DX2052]
PSD854F2@TQFP52 [DX3009]
PSD854F2@TQFP52(new) [DX3009]
PSD854F2V@PLCC52 [DX2052]
PSD854F2V@PLCC52(new) [DX2052]
PSD854F2V@TQFP52 [DX3009]
PSD854F2V@TQFP52(new) [DX3009]
ST62E01 [DX0001]
ST62E01@SOIC16 [DX1033]
ST62E01CF1 [DX0001]
ST62E20 [DX0001]
ST62E20@SOIC20 [DX1033]
ST62E20CF1 [DX0001]
ST62E25 [DX1033]
ST62E25@SOIC28 [DX1033]
ST62E25CF1 [DX0001]
ST62E60B [DX0001]
ST62E60B@SOIC20 [DX1036]
ST62E62CF1 [DX0001]
ST62E65B [DX0001]
ST62E65B@SOIC28 [DX1036]
ST62E65CF1 [DX0001]
ST62T00 [DX0001]

ST62T00@SOIC16 [DX1033]
ST62T00C(B6) [DX0001]
ST62T00C(M6)@SOIC16 [DX1033]
ST62T00C(N6)@SSOP16 [DX1026]
ST62T01 [DX0001]
ST62T01@SOIC16 [DX1033]
ST62T01C(B3) [DX0001]
ST62T01C(B6) [DX0001]
ST62T01C(M3)@SOIC16 [DX1033]
ST62T01C(M6)@SOIC16 [DX1033]
ST62T01C(N3)@SSOP16 [DX1026]
ST62T01C(N6)@SSOP16 [DX1026]
ST62T03 [DX0001]
ST62T03@SOIC16 [DX1033]
ST62T03C(B6) [DX0001]
ST62T03C(M3)@SOIC16 [DX1033]
ST62T03C(M6)@SOIC16 [DX1033]
ST62T03C(N6)@SSOP16 [DX1026]
ST62T08 [DX0001]
ST62T08@SOIC20 [DX1033]
ST62T08C(B6) [DX0001]
ST62T08C(M6)@SOIC20 [DX1033]
ST62T09 [DX0001]
ST62T09@SOIC20 [DX1033]
ST62T09C(B3) [DX0001]
ST62T09C(B6) [DX0001]
ST62T09C(M3)@SOIC20 [DX1033]
ST62T09C(M6)@SOIC20 [DX1033]
ST62T10 [DX0001]
ST62T10@SOIC20 [DX1033]
ST62T10C(B6) [DX0001]
ST62T10C(M6)@SOIC20 [DX1033]
ST62T15 [DX0001]
ST62T15@SOIC28 [DX1033]
ST62T15C(B6) [DX0001]
ST62T15C(M6)@SOIC28 [DX1033]
ST62T20 [DX0001]
ST62T20@SOIC20 [DX1033]
ST62T20C(B3) [DX0001]
ST62T20C(B6) [DX0001]
ST62T20C(M3)@SOIC20 [DX1033]
ST62T20C(M6)@SOIC20 [DX1033]
ST62T25 [DX0001]
ST62T25@SOIC28 [DX1033]
ST62T25C(B3) [DX0001]
ST62T25C(B6) [DX0001]
ST62T25C(M3)@SOIC28 [DX1033]
ST62T25C(M6)@SOIC28 [DX1033]
ST62T25C(N6)@SSOP28 [DX1026]
ST62T53B [DX0001]
ST62T53B@SOIC20 [DX1036]
ST62T60B [DX0001]
ST62T60B@SOIC20 [DX1036]
ST62T60C6 [DX0001]
ST62T62C(B6) [DX0001]
ST62T62C(M3)@SOIC16 [DX1033]
ST62T62C(M6)@SOIC16 [DX1033]
ST62T62C(N3)@SSOP16 [DX1026]
ST62T62C(N6)@SSOP16 [DX1026]
ST62T63B [DX0001]
ST62T63B@SOIC20 [DX1036]
ST62T63C(B6) [DX0001]
ST62T63C(M6)@SOIC20 [DX1033]
ST62T65B [DX0001]
ST62T65B@SOIC28 [DX1036]
ST62T65C(B3) [DX0001]
ST62T65C(B6) [DX0001]
ST62T65C(M3)@SOIC28 [DX1033]
ST62T65C(M6)@SOIC28 [DX1033]
ST62T65C(N6)@SSOP28 [DX1026]
ST72C104G1B@SDIP32 [DX0032]
ST72C104G1M@SOIC28 [DX1033]
ST72C104G2B@SDIP32 [DX0032]
ST72C104G2M@SOIC28 [DX1033]
ST72C124J2B@SDIP42 [DX0042]
ST72C124J2T@TQFP44 [DX3003]
ST72C124J4B@SDIP42 [DX0042]
ST72C124J4T@TQFP44 [DX3003]
ST72C215G1B@SDIP32 [DX0032]
ST72C215G1M@SOIC28 [DX1033]
ST72C215G2B@SDIP32 [DX0032]
ST72C215G2M@SOIC28 [DX1033]
ST72C216G1B@SDIP32 [DX0032]
ST72C216G1M@SOIC28 [DX1033]
ST72C216G2B@SDIP32 [DX0032]
ST72C216G2M@SOIC28 [DX1033]
ST72C254G1B@SDIP32 [DX0032]
ST72C254G1M@SOIC28 [DX1033]
ST72C254G2B@SDIP32 [DX0032]
ST72C254G2M@SOIC28 [DX1033]
ST72C314J2B@SDIP42 [DX0042]
ST72C314J2T@TQFP44 [DX3003]
ST72C314J4B@SDIP42 [DX0042]
ST72C314J4T@TQFP44 [DX3003]
ST72C314N2B@SDIP56 [DX0056]
ST72C314N2T@TQFP64 [DX0056]

ST72C314N4B@SDIP56 [DX0056]
ST72C314N4T@TQFP64 [DX0056]
ST72C334J2B@SDIP42 [DX0042]
ST72C334J2T@TQFP44 [DX3003]
ST72C334J4B@SDIP42 [DX0042]
ST72C334J4T@TQFP44 [DX3003]
ST72C334N2B@SDIP56 [DX0056]
ST72C334N2T@TQFP64 [DX0056]
ST72C334N4B@SDIP56 [DX0056]
ST72C334N4T@TQFP64 [DX3013]
ST72F260G1B6@SDIP32 [DX0032]
ST72F260G1M6@SOIC28 [DX1033]
ST72F260G2B6@SDIP32 [DX0032]
ST72F260G2H1@LFBGA36 [DX5063]
ST72F260G2H6@LFBGA36 [DX5063]
ST72F260G2M6@SOIC28 [DX1033]
ST72F262G1B6@SDIP32 [DX0032]
ST72F262G1M6@SOIC28 [DX1033]
ST72F262G2B6@SDIP32 [DX0032]
ST72F262G2H1@LFBGA36 [DX5063]
ST72F262G2H6@LFBGA36 [DX5063]
ST72F262G2M6@SOIC28 [DX1033]
ST72F264G1B6@SDIP32 [DX0032]
ST72F264G1M6@SOIC28 [DX1033]
ST72F264G2B6@SDIP32 [DX0032]
ST72F264G2H1@LFBGA36 [DX5063]
ST72F264G2H6@LFBGA36 [DX5063]
ST72F264G2M6@SOIC28 [DX1033]
ST72F321AR6T3@TQFP64 [DX3011]
ST72F321AR6T6@TQFP64 [DX3011]
ST72F321AR6TA@TQFP64 [DX3011]
ST72F321AR7T3@TQFP64 [DX3011]
ST72F321AR7T6@TQFP64 [DX3011]
ST72F321AR7TA@TQFP64 [DX3011]
ST72F321AR9T3@TQFP64 [DX3011]
ST72F321AR9T6@TQFP64 [DX3011]
ST72F321AR9TA@TQFP64 [DX3011]
ST72F321AR9TC@TQFP64 [DX3011]
ST72F321BAR6T3@TQFP64 [DX3011]
ST72F321BAR6T6@TQFP64 [DX3011]
ST72F321BAR6TA@TQFP64 [DX3011]
ST72F321BAR7T3@TQFP64 [DX3011]
ST72F321BAR7T6@TQFP64 [DX3011]
ST72F321BAR7TA@TQFP64 [DX3011]
ST72F321BAR9T3@TQFP64 [DX3011]
ST72F321BAR9T6@TQFP64 [DX3011]
ST72F321BAR9TA@TQFP64 [DX3011]
ST72F321BAR9TC@TQFP64 [DX3011]
ST72F321BJ6T3@TQFP44 [DX3003]
ST72F321BJ6T6@TQFP44 [DX3003]
ST72F321BJ6TA@TQFP44 [DX3003]
ST72F321BJ7T3@TQFP44 [DX3003]
ST72F321BJ7T6@TQFP44 [DX3003]
ST72F321BJ7TA@TQFP44 [DX3003]
ST72F321BJ9T3@TQFP44 [DX3003]
ST72F321BJ9T6@TQFP44 [DX3003]
ST72F321BJ9TA@TQFP44 [DX3003]
ST72F321BJ9TC@TQFP44 [DX3003]
ST72F321BM9T3@TQFP80 [DX3054]
ST72F321BM9T6@TQFP80 [DX3054]
ST72F321BM9TC@TQFP80 [DX3054]
ST72F321BR6T3@TQFP64 [DX3013]
ST72F321BR6T6@TQFP64 [DX3013]
ST72F321BR6TA@TQFP64 [DX3013]
ST72F321BR7T3@TQFP64 [DX3013]
ST72F321BR7T6@TQFP64 [DX3013]
ST72F321BR7TA@TQFP64 [DX3013]
ST72F321BR9T3@TQFP64 [DX3013]
ST72F321BR9T6@TQFP64 [DX3013]
ST72F321BR9TA@TQFP64 [DX3013]
ST72F321BR9TC@TQFP64 [DX3013]
ST72F321J6T3@TQFP44 [DX3003]
ST72F321J6T6@TQFP44 [DX3003]
ST72F321J6TA@TQFP44 [DX3003]
ST72F321J7T3@TQFP44 [DX3003]
ST72F321J7T6@TQFP44 [DX3003]
ST72F321J7TA@TQFP44 [DX3003]
ST72F321J9T3@TQFP44 [DX3003]
ST72F321J9T6@TQFP44 [DX3003]
ST72F321J9TA@TQFP44 [DX3003]
ST72F321J9TC@TQFP44 [DX3003]
ST72F321M9T3@TQFP80 [DX3054]
ST72F321M9T6@TQFP80 [DX3054]
ST72F321M9TC@TQFP80 [DX3054]
ST72F321R6T3@TQFP64 [DX3013]
ST72F321R6T6@TQFP64 [DX3013]
ST72F321R6TA@TQFP64 [DX3013]
ST72F321R7T3@TQFP64 [DX3013]
ST72F321R7T6@TQFP64 [DX3013]
ST72F321R7TA@TQFP64 [DX3013]
ST72F321R9T3@TQFP64 [DX3013]
ST72F321R9T6@TQFP64 [DX3013]
ST72F321R9TA@TQFP64 [DX3013]
ST72F321R9TC@TQFP64 [DX3013]
ST72F324BJ2B3@SDIP42 [DX0042]

ST72F324BJ2B3@SDIP42(new) [DX0042]
ST72F324BJ2B5@SDIP42 [DX0042]
ST72F324BJ2B5@SDIP42(new) [DX0042]
ST72F324BJ2B6@SDIP42 [DX0042]
ST72F324BJ2B6@SDIP42(new) [DX0042]
ST72F324BJ2BA@SDIP42 [DX0042]
ST72F324BJ2BA@SDIP42(new) [DX0042]
ST72F324BJ2BC@SDIP42 [DX0042]
ST72F324BJ2BC@SDIP42(new) [DX0042]
ST72F324BJ2T3@TQFP44 [DX3003]
ST72F324BJ2T3@TQFP44(new) [DX3003]
ST72F324BJ2T5@TQFP44 [DX3003]
ST72F324BJ2T5@TQFP44(new) [DX3003]
ST72F324BJ2T6@TQFP44 [DX3003]
ST72F324BJ2T6@TQFP44(new) [DX3003]
ST72F324BJ2TA@TQFP44 [DX3003]
ST72F324BJ2TA@TQFP44(new) [DX3003]
ST72F324BJ2TC@TQFP44 [DX3003]
ST72F324BJ2TC@TQFP44(new) [DX3003]
ST72F324BJ4B3@SDIP42 [DX0042]
ST72F324BJ4B3@SDIP42(new) [DX0042]
ST72F324BJ4B5@SDIP42 [DX0042]
ST72F324BJ4B5@SDIP42(new) [DX0042]
ST72F324BJ4B6@SDIP42 [DX0042]
ST72F324BJ4B6@SDIP42(new) [DX0042]
ST72F324BJ4BA@SDIP42 [DX0042]
ST72F324BJ4BA@SDIP42(new) [DX0042]
ST72F324BJ4BC@SDIP42 [DX0042]
ST72F324BJ4BC@SDIP42(new) [DX0042]
ST72F324BJ4T3@TQFP44 [DX3003]
ST72F324BJ4T3@TQFP44(new) [DX3003]
ST72F324BJ4T5@TQFP44 [DX3003]
ST72F324BJ4T5@TQFP44(new) [DX3003]
ST72F324BJ4T6@TQFP44 [DX3003]
ST72F324BJ4T6@TQFP44(new) [DX3003]
ST72F324BJ4TA@TQFP44 [DX3003]
ST72F324BJ4TA@TQFP44(new) [DX3003]
ST72F324BJ4TC@TQFP44 [DX3003]
ST72F324BJ4TC@TQFP44(new) [DX3003]
ST72F324BJ6B3@SDIP42 [DX0042]
ST72F324BJ6B3@SDIP42(new) [DX0042]
ST72F324BJ6B5@SDIP42 [DX0042]
ST72F324BJ6B5@SDIP42(new) [DX0042]
ST72F324BJ6B6@SDIP42 [DX0042]
ST72F324BJ6B6@SDIP42(new) [DX0042]
ST72F324BJ6BA@SDIP42 [DX0042]
ST72F324BJ6BA@SDIP42(new) [DX0042]
ST72F324BJ6BC@SDIP42 [DX0042]

ST72F324BJ6BC@SDIP42(new) [DX0042]
ST72F324BJ6T3@TQFP44 [DX3003]
ST72F324BJ6T3@TQFP44(new) [DX3003]
ST72F324BJ6T5@TQFP44 [DX3003]
ST72F324BJ6T5@TQFP44(new) [DX3003]
ST72F324BJ6T6@TQFP44 [DX3003]
ST72F324BJ6T6@TQFP44(new) [DX3003]
ST72F324BJ6TA@TQFP44 [DX3003]
ST72F324BJ6TA@TQFP44(new) [DX3003]
ST72F324BJ6TC@TQFP44 [DX3003]
ST72F324BJ6TC@TQFP44(new) [DX3003]
ST72F324BK2B3@SDIP32 [DX0032]
ST72F324BK2B3@SDIP32(new) [DX0032]
ST72F324BK2B5@SDIP32 [DX0032]
ST72F324BK2B5@SDIP32(new) [DX0032]
ST72F324BK2B6@SDIP32 [DX0032]
ST72F324BK2B6@SDIP32(new) [DX0032]
ST72F324BK2BA@SDIP32 [DX0032]
ST72F324BK2BA@SDIP32(new) [DX0032]
ST72F324BK2BC@SDIP32 [DX0032]
ST72F324BK2BC@SDIP32(new) [DX0032]
ST72F324BK2T3@TQFP32 [DX3001]
ST72F324BK2T3@TQFP32(new) [DX3001]
ST72F324BK2T5@TQFP32 [DX3001]
ST72F324BK2T5@TQFP32(new) [DX3001]
ST72F324BK2T6@TQFP32 [DX3001]
ST72F324BK2T6@TQFP32(new) [DX3001]
ST72F324BK2TA@TQFP32 [DX3001]
ST72F324BK2TA@TQFP32(new) [DX3001]
ST72F324BK2TC@TQFP32 [DX3001]
ST72F324BK2TC@TQFP32(new) [DX3001]
ST72F324BK4B3@SDIP32 [DX0032]
ST72F324BK4B3@SDIP32(new) [DX0032]
ST72F324BK4B5@SDIP32 [DX0032]
ST72F324BK4B5@SDIP32(new) [DX0032]
ST72F324BK4B6@SDIP32 [DX0032]
ST72F324BK4B6@SDIP32(new) [DX0032]
ST72F324BK4BA@SDIP32 [DX0032]
ST72F324BK4BA@SDIP32(new) [DX0032]
ST72F324BK4BC@SDIP32 [DX0032]
ST72F324BK4BC@SDIP32(new) [DX0032]
ST72F324BK4T3@TQFP32 [DX3001]
ST72F324BK4T3@TQFP32(new) [DX3001]
ST72F324BK4T5@TQFP32 [DX3001]
ST72F324BK4T5@TQFP32(new) [DX3001]
ST72F324BK4T6@TQFP32 [DX3001]
ST72F324BK4T6@TQFP32(new) [DX3001]
ST72F324BK4TA@TQFP32 [DX3001]

ST72F324BK4TA@TQFP32(new) [DX3001]
ST72F324BK4TC@TQFP32 [DX3001]
ST72F324BK4TC@TQFP32(new) [DX3001]
ST72F324BK6B3@SDIP32 [DX0032]
ST72F324BK6B3@SDIP32(new) [DX0032]
ST72F324BK6B5@SDIP32 [DX0032]
ST72F324BK6B5@SDIP32(new) [DX0032]
ST72F324BK6B6@SDIP32 [DX0032]
ST72F324BK6B6@SDIP32(new) [DX0032]
ST72F324BK6BA@SDIP32 [DX0032]
ST72F324BK6BA@SDIP32(new) [DX0032]
ST72F324BK6BC@SDIP32 [DX0032]
ST72F324BK6BC@SDIP32(new) [DX0032]
ST72F324BK6T3@TQFP32 [DX3001]
ST72F324BK6T3@TQFP32(new) [DX3001]
ST72F324BK6T5@TQFP32 [DX3001]
ST72F324BK6T5@TQFP32(new) [DX3001]
ST72F324BK6T6@TQFP32 [DX3001]
ST72F324BK6T6@TQFP32(new) [DX3001]
ST72F324BK6TA@TQFP32 [DX3001]
ST72F324BK6TA@TQFP32(new) [DX3001]
ST72F324BK6TC@TQFP32 [DX3001]
ST72F324BK6TC@TQFP32(new) [DX3001]
ST72F324J2B3@SDIP42 [DX0042]
ST72F324J2B3@SDIP42(new) [DX0042]
ST72F324J2B5@SDIP42 [DX0042]
ST72F324J2B5@SDIP42(new) [DX0042]
ST72F324J2B6@SDIP42 [DX0042]
ST72F324J2B6@SDIP42(new) [DX0042]
ST72F324J2BA@SDIP42 [DX0042]
ST72F324J2BA@SDIP42(new) [DX0042]
ST72F324J2BC@SDIP42 [DX0042]
ST72F324J2BC@SDIP42(new) [DX0042]
ST72F324J2T3@TQFP44 [DX3003]
ST72F324J2T3@TQFP44(new) [DX3003]
ST72F324J2T5@TQFP44 [DX3003]
ST72F324J2T5@TQFP44(new) [DX3003]
ST72F324J2T6@TQFP44 [DX3003]
ST72F324J2T6@TQFP44(new) [DX3003]
ST72F324J2TA@TQFP44 [DX3003]
ST72F324J2TA@TQFP44(new) [DX3003]
ST72F324J2TC@TQFP44 [DX3003]
ST72F324J2TC@TQFP44(new) [DX3003]
ST72F324J4B3@SDIP42 [DX0042]
ST72F324J4B3@SDIP42(new) [DX0042]
ST72F324J4B5@SDIP42 [DX0042]
ST72F324J4B5@SDIP42(new) [DX0042]
ST72F324J4B6@SDIP42 [DX0042]

ST72F324J4B6@SDIP42(new) [DX0042]
ST72F324J4BA@SDIP42 [DX0042]
ST72F324J4BA@SDIP42(new) [DX0042]
ST72F324J4BC@SDIP42 [DX0042]
ST72F324J4BC@SDIP42(new) [DX0042]
ST72F324J4T3@TQFP44 [DX3003]
ST72F324J4T3@TQFP44(new) [DX3003]
ST72F324J4T5@TQFP44 [DX3003]
ST72F324J4T5@TQFP44(new) [DX3003]
ST72F324J4T6@TQFP44 [DX3003]
ST72F324J4T6@TQFP44(new) [DX3003]
ST72F324J4TA@TQFP44 [DX3003]
ST72F324J4TA@TQFP44(new) [DX3003]
ST72F324J4TC@TQFP44 [DX3003]
ST72F324J4TC@TQFP44(new) [DX3003]
ST72F324J6B3@SDIP42 [DX0042]
ST72F324J6B3@SDIP42(new) [DX0042]
ST72F324J6B5@SDIP42 [DX0042]
ST72F324J6B5@SDIP42(new) [DX0042]
ST72F324J6B6@SDIP42 [DX0042]
ST72F324J6B6@SDIP42(new) [DX0042]
ST72F324J6BA@SDIP42 [DX0042]
ST72F324J6BA@SDIP42(new) [DX0042]
ST72F324J6BC@SDIP42 [DX0042]
ST72F324J6BC@SDIP42(new) [DX0042]
ST72F324J6T3@TQFP44 [DX3003]
ST72F324J6T3@TQFP44(new) [DX3003]
ST72F324J6T5@TQFP44 [DX3003]
ST72F324J6T5@TQFP44(new) [DX3003]
ST72F324J6T6@TQFP44 [DX3003]
ST72F324J6T6@TQFP44(new) [DX3003]
ST72F324J6TA@TQFP44 [DX3003]
ST72F324J6TA@TQFP44(new) [DX3003]
ST72F324J6TC@TQFP44 [DX3003]
ST72F324J6TC@TQFP44(new) [DX3003]
ST72F324K2B3@SDIP32 [DX0032]
ST72F324K2B3@SDIP32(new) [DX0032]
ST72F324K2B5@SDIP32 [DX0032]
ST72F324K2B5@SDIP32(new) [DX0032]
ST72F324K2B6@SDIP32 [DX0032]
ST72F324K2B6@SDIP32(new) [DX0032]
ST72F324K2BA@SDIP32 [DX0032]
ST72F324K2BA@SDIP32(new) [DX0032]
ST72F324K2BC@SDIP32 [DX0032]
ST72F324K2BC@SDIP32(new) [DX0032]
ST72F324K2T3@TQFP32 [DX3001]
ST72F324K2T3@TQFP32(new) [DX3001]
ST72F324K2T5@TQFP32 [DX3001]

ST72F324K2T5@TQFP32(new) [DX3001]
ST72F324K2T6@TQFP32 [DX3001]
ST72F324K2T6@TQFP32(new) [DX3001]
ST72F324K2TA@TQFP32 [DX3001]
ST72F324K2TA@TQFP32(new) [DX3001]
ST72F324K2TC@TQFP32 [DX3001]
ST72F324K2TC@TQFP32(new) [DX3001]
ST72F324K4B3@SDIP32 [DX0032]
ST72F324K4B3@SDIP32(new) [DX0032]
ST72F324K4B5@SDIP32 [DX0032]
ST72F324K4B5@SDIP32(new) [DX0032]
ST72F324K4B6@SDIP32 [DX0032]
ST72F324K4B6@SDIP32(new) [DX0032]
ST72F324K4BA@SDIP32 [DX0032]
ST72F324K4BA@SDIP32(new) [DX0032]
ST72F324K4BC@SDIP32 [DX0032]
ST72F324K4BC@SDIP32(new) [DX0032]
ST72F324K4T3@TQFP32 [DX3001]
ST72F324K4T3@TQFP32(new) [DX3001]
ST72F324K4T5@TQFP32 [DX3001]
ST72F324K4T5@TQFP32(new) [DX3001]
ST72F324K4T6@TQFP32 [DX3001]
ST72F324K4T6@TQFP32(new) [DX3001]
ST72F324K4TA@TQFP32 [DX3001]
ST72F324K4TA@TQFP32(new) [DX3001]
ST72F324K4TC@TQFP32 [DX3001]
ST72F324K4TC@TQFP32(new) [DX3001]
ST72F324K6B3@SDIP32 [DX0032]
ST72F324K6B3@SDIP32(new) [DX0032]
ST72F324K6B5@SDIP32 [DX0032]
ST72F324K6B5@SDIP32(new) [DX0032]
ST72F324K6B6@SDIP32 [DX0032]
ST72F324K6B6@SDIP32(new) [DX0032]
ST72F324K6BA@SDIP32 [DX0032]
ST72F324K6BA@SDIP32(new) [DX0032]
ST72F324K6BC@SDIP32 [DX0032]
ST72F324K6BC@SDIP32(new) [DX0032]
ST72F324K6T3@TQFP32 [DX3001]
ST72F324K6T3@TQFP32(new) [DX3001]
ST72F324K6T5@TQFP32 [DX3001]
ST72F324K6T5@TQFP32(new) [DX3001]
ST72F324K6T6@TQFP32 [DX3001]
ST72F324K6T6@TQFP32(new) [DX3001]
ST72F324K6TA@TQFP32 [DX3001]
ST72F324K6TA@TQFP32(new) [DX3001]
ST72F324K6TC@TQFP32 [DX3001]
ST72F324K6TC@TQFP32(new) [DX3001]
ST72F324LJ2B3@SDIP42 [DX0042]

ST72F324LJ2B3@SDIP42(new) [DX0042]
ST72F324LJ2B5@SDIP42 [DX0042]
ST72F324LJ2B5@SDIP42(new) [DX0042]
ST72F324LJ2B6@SDIP42 [DX0042]
ST72F324LJ2B6@SDIP42(new) [DX0042]
ST72F324LJ2BA@SDIP42 [DX0042]
ST72F324LJ2BA@SDIP42(new) [DX0042]
ST72F324LJ2BC@SDIP42 [DX0042]
ST72F324LJ2BC@SDIP42(new) [DX0042]
ST72F324LJ2T3@TQFP44 [DX3003]
ST72F324LJ2T3@TQFP44(new) [DX3003]
ST72F324LJ2T5@TQFP44 [DX3003]
ST72F324LJ2T5@TQFP44(new) [DX3003]
ST72F324LJ2T6@TQFP44 [DX3003]
ST72F324LJ2T6@TQFP44(new) [DX3003]
ST72F324LJ2TA@TQFP44 [DX3003]
ST72F324LJ2TA@TQFP44(new) [DX3003]
ST72F324LJ2TC@TQFP44 [DX3003]
ST72F324LJ2TC@TQFP44(new) [DX3003]
ST72F324LJ4B3@SDIP42 [DX0042]
ST72F324LJ4B3@SDIP42(new) [DX0042]
ST72F324LJ4B5@SDIP42 [DX0042]
ST72F324LJ4B5@SDIP42(new) [DX0042]
ST72F324LJ4B6@SDIP42 [DX0042]
ST72F324LJ4B6@SDIP42(new) [DX0042]
ST72F324LJ4BA@SDIP42 [DX0042]
ST72F324LJ4BA@SDIP42(new) [DX0042]
ST72F324LJ4BC@SDIP42 [DX0042]
ST72F324LJ4BC@SDIP42(new) [DX0042]
ST72F324LJ4T3@TQFP44 [DX3003]
ST72F324LJ4T3@TQFP44(new) [DX3003]
ST72F324LJ4T5@TQFP44 [DX3003]
ST72F324LJ4T5@TQFP44(new) [DX3003]
ST72F324LJ4T6@TQFP44 [DX3003]
ST72F324LJ4T6@TQFP44(new) [DX3003]
ST72F324LJ4TA@TQFP44 [DX3003]
ST72F324LJ4TA@TQFP44(new) [DX3003]
ST72F324LJ4TC@TQFP44 [DX3003]
ST72F324LJ4TC@TQFP44(new) [DX3003]
ST72F324LJ6B3@SDIP42 [DX0042]
ST72F324LJ6B3@SDIP42(new) [DX0042]
ST72F324LJ6B5@SDIP42 [DX0042]
ST72F324LJ6B5@SDIP42(new) [DX0042]
ST72F324LJ6B6@SDIP42 [DX0042]
ST72F324LJ6B6@SDIP42(new) [DX0042]
ST72F324LJ6BA@SDIP42 [DX0042]
ST72F324LJ6BA@SDIP42(new) [DX0042]
ST72F324LJ6BC@SDIP42 [DX0042]

ST72F324LJ6BC@SDIP42(new) [DX0042]
ST72F324LJ6T3@TQFP44 [DX3003]
ST72F324LJ6T3@TQFP44(new) [DX3003]
ST72F324LJ6T5@TQFP44 [DX3003]
ST72F324LJ6T5@TQFP44(new) [DX3003]
ST72F324LJ6T6@TQFP44 [DX3003]
ST72F324LJ6T6@TQFP44(new) [DX3003]
ST72F324LJ6TA@TQFP44 [DX3003]
ST72F324LJ6TA@TQFP44(new) [DX3003]
ST72F324LJ6TC@TQFP44 [DX3003]
ST72F324LJ6TC@TQFP44(new) [DX3003]
ST72F324LK2B3@SDIP32 [DX0032]
ST72F324LK2B3@SDIP32(new) [DX0032]
ST72F324LK2B5@SDIP32 [DX0032]
ST72F324LK2B5@SDIP32(new) [DX0032]
ST72F324LK2B6@SDIP32 [DX0032]
ST72F324LK2B6@SDIP32(new) [DX0032]
ST72F324LK2BA@SDIP32 [DX0032]
ST72F324LK2BA@SDIP32(new) [DX0032]
ST72F324LK2BC@SDIP32 [DX0032]
ST72F324LK2BC@SDIP32(new) [DX0032]
ST72F324LK2T3@TQFP32 [DX3001]
ST72F324LK2T3@TQFP32(new) [DX3001]
ST72F324LK2T5@TQFP32 [DX3001]
ST72F324LK2T5@TQFP32(new) [DX3001]
ST72F324LK2T6@TQFP32 [DX3001]
ST72F324LK2T6@TQFP32(new) [DX3001]
ST72F324LK2TA@TQFP32 [DX3001]
ST72F324LK2TA@TQFP32(new) [DX3001]
ST72F324LK2TC@TQFP32 [DX3001]
ST72F324LK2TC@TQFP32(new) [DX3001]
ST72F324LK4B3@SDIP32 [DX0032]
ST72F324LK4B3@SDIP32(new) [DX0032]
ST72F324LK4B5@SDIP32 [DX0032]
ST72F324LK4B5@SDIP32(new) [DX0032]
ST72F324LK4B6@SDIP32 [DX0032]
ST72F324LK4B6@SDIP32(new) [DX0032]
ST72F324LK4BA@SDIP32 [DX0032]
ST72F324LK4BA@SDIP32(new) [DX0032]
ST72F324LK4BC@SDIP32 [DX0032]
ST72F324LK4BC@SDIP32(new) [DX0032]
ST72F324LK4T3@TQFP32 [DX3001]
ST72F324LK4T3@TQFP32(new) [DX3001]
ST72F324LK4T5@TQFP32 [DX3001]
ST72F324LK4T5@TQFP32(new) [DX3001]
ST72F324LK4T6@TQFP32 [DX3001]
ST72F324LK4T6@TQFP32(new) [DX3001]
ST72F324LK4TA@TQFP32 [DX3001]

ST72F324LK4TA@TQFP32(new) [DX3001]
ST72F324LK4TC@TQFP32 [DX3001]
ST72F324LK4TC@TQFP32(new) [DX3001]
ST72F324LK6B3@SDIP32 [DX0032]
ST72F324LK6B3@SDIP32(new) [DX0032]
ST72F324LK6B5@SDIP32 [DX0032]
ST72F324LK6B5@SDIP32(new) [DX0032]
ST72F324LK6B6@SDIP32 [DX0032]
ST72F324LK6B6@SDIP32(new) [DX0032]
ST72F324LK6BA@SDIP32 [DX0032]
ST72F324LK6BA@SDIP32(new) [DX0032]
ST72F324LK6BC@SDIP32 [DX0032]
ST72F324LK6BC@SDIP32(new) [DX0032]
ST72F324LK6T3@TQFP32 [DX3001]
ST72F324LK6T3@TQFP32(new) [DX3001]
ST72F324LK6T5@TQFP32 [DX3001]
ST72F324LK6T5@TQFP32(new) [DX3001]
ST72F324LK6T6@TQFP32 [DX3001]
ST72F324LK6T6@TQFP32(new) [DX3001]
ST72F324LK6TA@TQFP32 [DX3001]
ST72F324LK6TA@TQFP32(new) [DX3001]
ST72F324LK6TC@TQFP32 [DX3001]
ST72F324LK6TC@TQFP32(new) [DX3001]
ST72F325AR6T3@TQFP64 [DX3011]
ST72F325AR6T5@TQFP64 [DX3011]
ST72F325AR6T6@TQFP64 [DX3011]
ST72F325AR7T3@TQFP64 [DX3011]
ST72F325AR7T5@TQFP64 [DX3011]
ST72F325AR7T6@TQFP64 [DX3011]
ST72F325AR9T3@TQFP64 [DX3011]
ST72F325AR9T5@TQFP64 [DX3011]
ST72F325AR9T6@TQFP64 [DX3011]
ST72F325C4T3@TQFP48 [DX3007]
ST72F325C4T5@TQFP48 [DX3007]
ST72F325C4T6@TQFP48 [DX3007]
ST72F325C6T3@TQFP48 [DX3007]
ST72F325C6T5@TQFP48 [DX3007]
ST72F325C6T6@TQFP48 [DX3007]
ST72F325C7T3@TQFP48 [DX3007]
ST72F325C7T5@TQFP48 [DX3007]
ST72F325C7T6@TQFP48 [DX3007]
ST72F325C9T3@TQFP48 [DX3007]
ST72F325C9T5@TQFP48 [DX3007]
ST72F325C9T6@TQFP48 [DX3007]
ST72F325J4B3@SDIP42 [DX0042]
ST72F325J4B5@SDIP42 [DX0042]
ST72F325J4B6@SDIP42 [DX0042]
ST72F325J4T3@TQFP44 [DX3003]
ST72F325J4T5@TQFP44 [DX3003]
ST72F325J4T6@TQFP44 [DX3003]
ST72F325J6B3@SDIP42 [DX0042]
ST72F325J6B5@SDIP42 [DX0042]
ST72F325J6B6@SDIP42 [DX0042]
ST72F325J6T3@TQFP44 [DX3003]
ST72F325J6T5@TQFP44 [DX3003]
ST72F325J6T6@TQFP44 [DX3003]
ST72F325J7T3@TQFP44 [DX3003]
ST72F325J7T5@TQFP44 [DX3003]
ST72F325J7T6@TQFP44 [DX3003]
ST72F325J9T3@TQFP44 [DX3003]
ST72F325J9T5@TQFP44 [DX3003]
ST72F325J9T6@TQFP44 [DX3003]
ST72F325K4B3@SDIP32 [DX0032]
ST72F325K4B5@SDIP32 [DX0032]
ST72F325K4B6@SDIP32 [DX0032]
ST72F325K4T3@TQFP32 [DX3001]
ST72F325K4T5@TQFP32 [DX3001]
ST72F325K4T6@TQFP32 [DX3001]
ST72F325K6B3@SDIP32 [DX0032]
ST72F325K6B5@SDIP32 [DX0032]
ST72F325K6B6@SDIP32 [DX0032]
ST72F325K6T3@TQFP32 [DX3001]
ST72F325K6T5@TQFP32 [DX3001]

ST72F325K6T6@TQFP32 [DX3001]	ST72F325R6T3@TQFP64 [DX3013]
ST72F325R6T5@TQFP64 [DX3013]	ST72F325R6T6@TQFP64 [DX3013]
ST72F325R7T3@TQFP64 [DX3013]	ST72F325R7T5@TQFP64 [DX3013]
ST72F325R7T6@TQFP64 [DX3013]	ST72F325R9T3@TQFP64 [DX3013]
ST72F325R9T5@TQFP64 [DX3013]	ST72F325R9T6@TQFP64 [DX3013]
ST72F32AJ1B5@SDIP42 [DX0042]	ST72F32AJ1B6@SDIP42 [DX0042]
ST72F32AJ1T5@TQFP44 [DX3003]	ST72F32AJ1T6@TQFP44 [DX3003]
ST72F32AJ2B5@SDIP42 [DX0042]	ST72F32AJ2B6@SDIP42 [DX0042]
ST72F32AJ2T5@TQFP44 [DX3003]	ST72F32AJ2T6@TQFP44 [DX3003]
ST72F32AJ2TA@TQFP44 [DX3003]	ST72F32AJ2TB@TQFP44 [DX3003]
ST72F32AJ2TC@TQFP44 [DX3003]	ST72F32AK1B5@SDIP32 [DX0032]
ST72F32AK1B6@SDIP32 [DX0032]	ST72F32AK1T5@TQFP32 [DX3001]
ST72F32AK1T6@TQFP32 [DX3001]	ST72F32AK2B5@SDIP32 [DX0032]
ST72F32AK2B6@SDIP32 [DX0032]	ST72F32AK2T5@TQFP32 [DX3001]
ST72F32AK2T6@TQFP32 [DX3001]	ST72F32AK2TA@TQFP32 [DX3001]
ST72F32AK2TB@TQFP32 [DX3001]	ST72F32AK2TC@TQFP32 [DX3001]
ST72F340K2T6@TQFP32 [DX3001]	ST72F340K4T6@TQFP32 [DX3001]
ST72F340S2T6@TQFP44 [DX3003]	ST72F340S4T6@TQFP44 [DX3003]
ST72F344K2T6@TQFP32 [DX3001]	ST72F344K4T6@TQFP32 [DX3001]
ST72F344S2T6@TQFP44 [DX3003]	ST72F344S4T6@TQFP44 [DX3003]
ST72F345C2T6@TQFP48 [DX3007]	ST72F345C4T6@TQFP48 [DX3007]
ST72F361AR4T3@TQFP64 [DX3011]	ST72F361AR4T6@TQFP64 [DX3011]
ST72F361AR4TA@TQFP64 [DX3011]	ST72F361AR4TC@TQFP64 [DX3011]
ST72F361AR6T3@TQFP64 [DX3011]	ST72F361AR6T6@TQFP64 [DX3011]
ST72F361AR6TA@TQFP64 [DX3011]	ST72F361AR6TC@TQFP64 [DX3011]
ST72F361AR7T3@TQFP64 [DX3011]	ST72F361AR7T6@TQFP64 [DX3011]
ST72F361AR7TA@TQFP64 [DX3011]	ST72F361AR7TC@TQFP64 [DX3011]
ST72F361AR9T3@TQFP64 [DX3011]	ST72F361AR9T6@TQFP64 [DX3011]
ST72F361AR9TA@TQFP64 [DX3011]	ST72F361AR9TC@TQFP64 [DX3011]
ST72F361J4T3@TQFP44 [DX3003]	ST72F361J4T6@TQFP44 [DX3003]
ST72F361J4TA@TQFP44 [DX3003]	ST72F361J4TC@TQFP44 [DX3003]
ST72F361J6T3@TQFP44 [DX3003]	ST72F361J6T6@TQFP44 [DX3003]
ST72F361J6TA@TQFP44 [DX3003]	ST72F361J6TC@TQFP44 [DX3003]
ST72F361J7T3@TQFP44 [DX3003]	ST72F361J7T6@TQFP44 [DX3003]
ST72F361J7TA@TQFP44 [DX3003]	ST72F361J7TC@TQFP44 [DX3003]
ST72F361J9T3@TQFP44 [DX3003]	ST72F361J9T6@TQFP44 [DX3003]
ST72F361J9TA@TQFP44 [DX3003]	ST72F361J9TC@TQFP44 [DX3003]
ST72F361K4T3@TQFP32 [DX3001]	ST72F361K4T6@TQFP32 [DX3001]
ST72F361K4TA@TQFP32 [DX3001]	ST72F361K4TC@TQFP32 [DX3001]
ST72F361K6T3@TQFP32 [DX3001]	ST72F361K6T6@TQFP32 [DX3001]
ST72F361K6TA@TQFP32 [DX3001]	ST72F361K6TC@TQFP32 [DX3001]
ST72F361K7T3@TQFP32 [DX3001]	ST72F361K7T6@TQFP32 [DX3001]
ST72F361K7TA@TQFP32 [DX3001]	ST72F361K7TC@TQFP32 [DX3001]
ST72F361K9T3@TQFP32 [DX3001]	ST72F361K9T6@TQFP32 [DX3001]
ST72F361K9TA@TQFP32 [DX3001]	ST72F361K9TC@TQFP32 [DX3001]
ST72F361R4T3@TQFP64 [DX3012]	ST72F361R4T6@TQFP64 [DX3012]
ST72F361R4TA@TQFP64 [DX3012]	ST72F361R4TC@TQFP64 [DX3012]
ST72F361R6T3@TQFP64 [DX3012]	ST72F361R6T6@TQFP64 [DX3012]

ST72F361R6TA@TQFP64 [DX3012]
ST72F361R6TC@TQFP64 [DX3012]
ST72F361R7T3@TQFP64 [DX3012]
ST72F361R7T6@TQFP64 [DX3012]
ST72F361R7TA@TQFP64 [DX3012]
ST72F361R7TC@TQFP64 [DX3012]
ST72F361R9T3@TQFP64 [DX3012]
ST72F361R9T6@TQFP64 [DX3012]
ST72F361R9TA@TQFP64 [DX3012]
ST72F361R9TC@TQFP64 [DX3012]
ST72F521AR6T3@TQFP64 [DX3011]
ST72F521AR6T6@TQFP64 [DX3011]
ST72F521AR6TC@TQFP64 [DX3011]
ST72F521AR9T3@TQFP64 [DX3011]
ST72F521AR9T6@TQFP64 [DX3011]
ST72F521AR9TC@TQFP64 [DX3011]
ST72F521BAR6T3@TQFP64 [DX3011]
ST72F521BAR6T6@TQFP64 [DX3011]
ST72F521BAR6TC@TQFP64 [DX3011]
ST72F521BAR9T3@TQFP64 [DX3011]
ST72F521BAR9T6@TQFP64 [DX3011]
ST72F521BAR9TC@TQFP64 [DX3011]
ST72F521BM9T3@TQFP80 [DX3054]
ST72F521BM9T6@TQFP80 [DX3054]
ST72F521BM9TC@TQFP80 [DX3054]
ST72F521BR6T3@TQFP64 [DX3013]
ST72F521BR6T6@TQFP64 [DX3013]
ST72F521BR6TC@TQFP64 [DX3013]
ST72F521BR9T3@TQFP64 [DX3013]
ST72F521BR9T6@TQFP64 [DX3013]
ST72F521BR9TC@TQFP64 [DX3013]
ST72F521M9T3@TQFP80 [DX3054]
ST72F521M9T6@TQFP80 [DX3054]
ST72F521M9TC@TQFP80 [DX3054]
ST72F521R6T3@TQFP64 [DX3013]
ST72F521R6T6@TQFP64 [DX3013]
ST72F521R6TC@TQFP64 [DX3013]
ST72F521R9T3@TQFP64 [DX3013]
ST72F521R9T6@TQFP64 [DX3013]
ST72F521R9TC@TQFP64 [DX3013]
ST72F561AR4T3@TQFP64 [DX3011]
ST72F561AR4T6@TQFP64 [DX3011]
ST72F561AR4TA@TQFP64 [DX3011]
ST72F561AR4TC@TQFP64 [DX3011]
ST72F561AR6T3@TQFP64 [DX3011]
ST72F561AR6T6@TQFP64 [DX3011]
ST72F561AR6TA@TQFP64 [DX3011]
ST72F561AR6TC@TQFP64 [DX3011]
ST72F561AR7T3@TQFP64 [DX3011]
ST72F561AR7T6@TQFP64 [DX3011]
ST72F561AR7TA@TQFP64 [DX3011]
ST72F561AR7TC@TQFP64 [DX3011]
ST72F561AR9T3@TQFP64 [DX3011]
ST72F561AR9T6@TQFP64 [DX3011]
ST72F561AR9TA@TQFP64 [DX3011]
ST72F561AR9TC@TQFP64 [DX3011]
ST72F561J4T3@TQFP44 [DX3003]
ST72F561J4T6@TQFP44 [DX3003]
ST72F561J4TA@TQFP44 [DX3003]
ST72F561J4TC@TQFP44 [DX3003]
ST72F561J6T3@TQFP44 [DX3003]
ST72F561J6T6@TQFP44 [DX3003]
ST72F561J6TA@TQFP44 [DX3003]
ST72F561J6TC@TQFP44 [DX3003]
ST72F561J7T3@TQFP44 [DX3003]
ST72F561J7T6@TQFP44 [DX3003]
ST72F561J7TA@TQFP44 [DX3003]
ST72F561J7TC@TQFP44 [DX3003]
ST72F561J9T3@TQFP44 [DX3003]
ST72F561J9T6@TQFP44 [DX3003]
ST72F561J9TA@TQFP44 [DX3003]
ST72F561J9TC@TQFP44 [DX3003]
ST72F561K4T3@TQFP32 [DX3001]
ST72F561K4T6@TQFP32 [DX3001]
ST72F561K4TA@TQFP32 [DX3001]
ST72F561K4TC@TQFP32 [DX3001]
ST72F561K6T3@TQFP32 [DX3001]
ST72F561K6T6@TQFP32 [DX3001]
ST72F561K6TA@TQFP32 [DX3001]
ST72F561K6TC@TQFP32 [DX3001]
ST72F561K7T3@TQFP32 [DX3001]
ST72F561K7T6@TQFP32 [DX3001]
ST72F561K7TA@TQFP32 [DX3001]
ST72F561K7TC@TQFP32 [DX3001]
ST72F561K9T3@TQFP32 [DX3001]
ST72F561K9T6@TQFP32 [DX3001]
ST72F561K9TA@TQFP32 [DX3001]
ST72F561K9TC@TQFP32 [DX3001]
ST72F561R4T3@TQFP64 [DX3013]
ST72F561R4T6@TQFP64 [DX3013]
ST72F561R4TA@TQFP64 [DX3013]
ST72F561R4TC@TQFP64 [DX3013]
ST72F561R6T3@TQFP64 [DX3013]
ST72F561R6T6@TQFP64 [DX3013]
ST72F561R6TA@TQFP64 [DX3013]
ST72F561R6TC@TQFP64 [DX3013]

ST72F561R7T3@TQFP64 [DX3013]
ST72F561R7T6@TQFP64 [DX3013]
ST72F561R7TA@TQFP64 [DX3013]
ST72F561R7TC@TQFP64 [DX3013]
ST72F561R9T3@TQFP64 [DX3013]
ST72F561R9T6@TQFP64 [DX3013]
ST72F561R9TA@TQFP64 [DX3013]
ST72F561R9TC@TQFP64 [DX3013]
ST72F60BD4U1@QFN40 [DX4017]
ST72F60BD6U1@QFN40 [DX4017]
ST72F60BE1M1@SOIC24 [DX1033]
ST72F60BE2M1@SOIC24 [DX1033]
ST72F60BE4M1@SOIC24 [DX1033]
ST72F60BE6M1@SOIC24 [DX1033]
ST72F60BK1U1@QFN40 [DX4017]
ST72F60BK2U1@QFN40 [DX4017]
ST72F60D4U1@QFN40 [DX4017]
ST72F60D6U1@QFN40 [DX4017]
ST72F60E1M1@SOIC24 [DX1033]
ST72F60E2M1@SOIC24 [DX1033]
ST72F60E4M1@SOIC24 [DX1033]
ST72F60E6M1@SOIC24 [DX1033]
ST72F60K1U1@QFN40 [DX4017]
ST72F60K2U1@QFN40 [DX4017]
ST72F621J4B1@SDIP42 [DX0042]
ST72F621J4T1@TQFP44 [DX3003]
ST72F621K4B1@SDIP32 [DX0032]
ST72F621L4M1@SOIC34 [DX1037]
ST72F622L2M1@SOIC34 [DX1037]
ST72F623F2B1 [DX0001]
ST72F623F2M1@SOIC20 [DX1033]
ST72F63BD4U1@QFN40 [DX4017]
ST72F63BD6U1@QFN40 [DX4017]
ST72F63BE1M1@SOIC24 [DX1033]
ST72F63BE2M1@SOIC24 [DX1033]
ST72F63BE4M1@SOIC24 [DX1033]
ST72F63BE6M1@SOIC24 [DX1033]
ST72F63BH1T1@TQFP48 [DX3007]
ST72F63BH2T1@TQFP48 [DX3007]
ST72F63BH4T1@TQFP48 [DX3007]
ST72F63BH6T1@TQFP48 [DX3007]
ST72F63BK1B1@SDIP32 [DX0032]
ST72F63BK1M1@SOIC34 [DX1037]
ST72F63BK1U1@QFN40 [DX4017]
ST72F63BK2B1@SDIP32 [DX0032]
ST72F63BK2M1@SOIC34 [DX1037]
ST72F63BK2U1@QFN40 [DX4017]
ST72F63BK4B1@SDIP32 [DX0032]
ST72F63BK4M1@SOIC34 [DX1037]
ST72F63BK6B1@SDIP32 [DX0032]
ST72F63BK6M1@SOIC34 [DX1037]
ST72F63D4U1@QFN40 [DX4017]
ST72F63D6U1@QFN40 [DX4017]
ST72F63E1M1@SOIC24 [DX1033]
ST72F63E2M1@SOIC24 [DX1033]
ST72F63E4M1@SOIC24 [DX1033]
ST72F63E6M1@SOIC24 [DX1033]
ST72F63H1T1@TQFP48 [DX3007]
ST72F63H2T1@TQFP48 [DX3007]
ST72F63H4T1@TQFP48 [DX3007]
ST72F63H6T1@TQFP48 [DX3007]
ST72F63K1B1@SDIP32 [DX0032]
ST72F63K1M1@SOIC34 [DX1037]
ST72F63K1U1@QFN40 [DX4017]
ST72F63K2B1@SDIP32 [DX0032]
ST72F63K2M1@SOIC34 [DX1037]
ST72F63K2U1@QFN40 [DX4017]
ST72F63K4B1@SDIP32 [DX0032]
ST72F63K4M1@SOIC34 [DX1037]
ST72F63K6B1@SDIP32 [DX0032]
ST72F63K6M1@SOIC34 [DX1037]
ST72F651AR6T1@TQFP64 [DX3011]
ST72F651AR6T1E@TQFP64 [DX3011]
ST72F651R6T1@TQFP64 [DX3012]
ST72F651R6T1E@TQFP64 [DX3012]
ST7FAUDIO@TQFP64 [DX3011]
ST7FAUDIOAR6@TQFP64 [DX3011]
ST7FAUDIOAR9@TQFP64 [DX3011]
ST7FDALIF2M6@SOIC20 [DX1033]
ST7FDALIF2M6@SOIC20(ISP) [DX0001]
ST7FLI49MK1B6 [DX0032]
ST7FLI49MK1T6@QFP32 [DX3001]
ST7FLIT10BF0B3 [DX0001]
ST7FLIT10BF0B6 [DX0001]
ST7FLIT10BF0M3@SOIC20 [DX1033]
ST7FLIT10BF0M6@SOIC20 [DX1033]
ST7FLIT10BF1B3 [DX0001]
ST7FLIT10BF1B6 [DX0001]
ST7FLIT10BF1M3@SOIC20 [DX1033]
ST7FLIT10BF1M6@SOIC20 [DX1033]
ST7FLIT10BY0B3 [DX0001]
ST7FLIT10BY0B6 [DX0001]
ST7FLIT10BY0M3@SOIC16 [DX1016]
ST7FLIT10BY0M6@SOIC16 [DX1016]

ST7FLIT10BY1B3 [DX0001]
ST7FLIT10BY1B6 [DX0001]
ST7FLIT10BY1M3@SOIC16 [DX1016]
ST7FLIT10BY1M6@SOIC16 [DX1016]
ST7FLIT15BF0B3 [DX0001]
ST7FLIT15BF0B6 [DX0001]
ST7FLIT15BF0M3@SOIC20 [DX1033]
ST7FLIT15BF0M6@SOIC20 [DX1033]
ST7FLIT15BF1B3 [DX0001]
ST7FLIT15BF1B6 [DX0001]
ST7FLIT15BF1M3@SOIC20 [DX1033]
ST7FLIT15BF1M6@SOIC20 [DX1033]
ST7FLIT15BF1U6TR@QFN20 [DX4011]
ST7FLIT15BY0B3 [DX0001]
ST7FLIT15BY0B6 [DX0001]
ST7FLIT15BY0M3@SOIC16 [DX1016]
ST7FLIT15BY0M6@SOIC16 [DX1016]
ST7FLIT15BY1B3 [DX0001]
ST7FLIT15BY1B6 [DX0001]
ST7FLIT15BY1M3@SOIC16 [DX1016]
ST7FLIT15BY1M6@SOIC16 [DX1016]
ST7FLIT19BF0B3 [DX0001]
ST7FLIT19BF0B6 [DX0001]
ST7FLIT19BF0M3@SOIC20 [DX1033]
ST7FLIT19BF0M6@SOIC20 [DX1033]
ST7FLIT19BF1B3 [DX0001]
ST7FLIT19BF1B6 [DX0001]
ST7FLIT19BF1M3@SOIC20 [DX1033]
ST7FLIT19BF1M6@SOIC20 [DX1033]
ST7FLIT19BF1U6TR@QFN20 [DX4011]
ST7FLIT19BY0B3 [DX0001]
ST7FLIT19BY0B6 [DX0001]
ST7FLIT19BY0M3@SOIC16 [DX1016]
ST7FLIT19BY0M6@SOIC16 [DX1016]
ST7FLIT19BY1B3 [DX0001]
ST7FLIT19BY1B6 [DX0001]
ST7FLIT19BY1M3@SOIC16 [DX1016]
ST7FLIT19BY1M6@SOIC16 [DX1016]
ST7FLITE02B6 [DX0001]
ST7FLITE02B6(ISP) [DX0001]
ST7FLITE02M6@SOIC16 [DX1016]
ST7FLITE02M6@SOIC16(ISP) [DX0001]
ST7FLITE02Y0B6 [DX0001]
ST7FLITE02Y0B6(ISP) [DX0001]
ST7FLITE02Y0M6@SOIC16 [DX1016]
ST7FLITE02Y0M6@SOIC16(ISP) [DX0001]
ST7FLITE05B6 [DX0001]
ST7FLITE05B6(ISP) [DX0001]
ST7FLITE05M6@SOIC16 [DX1016]
ST7FLITE05M6@SOIC16(ISP) [DX0001]
ST7FLITE05Y0B6 [DX0001]
ST7FLITE05Y0B6(ISP) [DX0001]
ST7FLITE05Y0M6@SOIC16 [DX1016]
ST7FLITE05Y0M6@SOIC16(ISP) [DX0001]
ST7FLITE09B6 [DX0001]
ST7FLITE09B6(ISP) [DX0001]
ST7FLITE09M6@SOIC16 [DX1016]
ST7FLITE09M6@SOIC16(ISP) [DX0001]
ST7FLITE09Y0B6 [DX0001]
ST7FLITE09Y0B6(ISP) [DX0001]
ST7FLITE09Y0M6@SOIC16 [DX1016]
ST7FLITE09Y0M6@SOIC16(ISP) [DX0001]
ST7FLITE10F1B6 [DX0001]
ST7FLITE10F1B6(ISP) [DX0001]
ST7FLITE10F1M6@SOIC20 [DX1033]
ST7FLITE10F1M6@SOIC20(ISP) [DX0001]
ST7FLITE15F1B6 [DX0001]
ST7FLITE15F1B6(ISP) [DX0001]
ST7FLITE15F1M6@SOIC20 [DX1033]
ST7FLITE15F1M6@SOIC20(ISP) [DX0001]
ST7FLITE19F1B6 [DX0001]
ST7FLITE19F1B6(ISP) [DX0001]
ST7FLITE19F1M6@SOIC20 [DX1033]
ST7FLITE19F1M6@SOIC20(ISP) [DX0001]
ST7FLITE20F2B6 [DX0001]
ST7FLITE20F2B6(ISP) [DX0001]
ST7FLITE20F2M6@SOIC20 [DX1033]

ST7FLITE20F2M6@SOIC20(ISP) [DX0001]
ST7FLITE25F2B6 [DX0001]
ST7FLITE25F2B6(ISP) [DX0001]
ST7FLITE25F2M6@SOIC20 [DX1033]
ST7FLITE25F2M6@SOIC20(ISP) [DX0001]
ST7FLITE29F2B6 [DX0001]
ST7FLITE29F2B6(ISP) [DX0001]
ST7FLITE29F2M6@SOIC20 [DX1033]
ST7FLITE29F2M6@SOIC20(ISP) [DX0001]
ST7FLITE30F2B6 [DX0001]
ST7FLITE30F2B6(ISP) [DX0001]
ST7FLITE30F2M6@SOIC20 [DX1033]
ST7FLITE30F2M6@SOIC20(ISP) [DX0001]
ST7FLITE33F2B6 [DX0001]
ST7FLITE33F2B6(ISP) [DX0001]
ST7FLITE33F2M6@SOIC20 [DX1033]
ST7FLITE33F2M6@SOIC20(ISP) [DX0001]
ST7FLITE35F2B6 [DX0001]
ST7FLITE35F2B6(ISP) [DX0001]
ST7FLITE35F2M6@SOIC20 [DX1033]
ST7FLITE35F2M6@SOIC20(ISP) [DX0001]
ST7FLITE39F2B6 [DX0001]
ST7FLITE39F2B6(ISP) [DX0001]
ST7FLITE39F2M6@SOIC20 [DX1033]
ST7FLITE39F2M6@SOIC20(ISP) [DX0001]
ST7FLITE49 [DX0032]
ST7FLITE49@QFN40 [DX4017]
ST7FLITE49@TQFP32 [DX3001]
ST7FLITEBC [DX0001]
ST7FLITEBCM6@SOIC16 [DX1016]
ST7FLITES0
ST7FLITES0@SOIC16 [DX1016]
ST7FLITES2B6 [DX0001]
ST7FLITES2B6(ISP) [DX0001]
ST7FLITES2M6@SOIC16 [DX1016]
ST7FLITES2M6@SOIC16(ISP) [DX0001]
ST7FLITES2Y0B6 [DX0001]
ST7FLITES2Y0B6(ISP) [DX0001]
ST7FLITES2Y0M6@SOIC16 [DX1016]
ST7FLITES2Y0M6@SOIC16(ISP) [DX0001]
ST7FLITES5B6 [DX0001]
ST7FLITES5B6(ISP) [DX0001]
ST7FLITES5M6@SOIC16 [DX1016]
ST7FLITES5M6@SOIC16(ISP) [DX0001]
ST7FLITES5Y0B6 [DX0001]
ST7FLITES5Y0B6(ISP) [DX0001]
ST7FLITES5Y0M6@SOIC16 [DX1016]
ST7FLITES5Y0M6@SOIC16(ISP) [DX0001]
ST7FMC1K2B3@SDIP32 [DX0032]
ST7FMC1K2B6@SDIP32 [DX0032]
ST7FMC1K2BC@SDIP32 [DX0032]
ST7FMC1K2T3@TQFP32 [DX3001]
ST7FMC1K2T6@TQFP32 [DX3001]
ST7FMC1K2TC@TQFP32 [DX3001]
ST7FMC1K4B3@SDIP32 [DX0032]
ST7FMC1K4B6@SDIP32 [DX0032]
ST7FMC1K4BC@SDIP32 [DX0032]
ST7FMC1K4T3@TQFP32 [DX3001]
ST7FMC1K4T6@TQFP32 [DX3001]
ST7FMC1K4TC@TQFP32 [DX3001]
ST7FMC1K6B3@SDIP32 [DX0032]
ST7FMC1K6B6@SDIP32 [DX0032]
ST7FMC1K6BC@SDIP32 [DX0032]
ST7FMC1K6T3@TQFP32 [DX3001]
ST7FMC1K6T6@TQFP32 [DX3001]
ST7FMC1K6TC@TQFP32 [DX3001]
ST7FMC2M9T3@TQFP80 [DX3054]
ST7FMC2M9T6@TQFP80 [DX3054]
ST7FMC2M9TC@TQFP80 [DX3054]
ST7FMC2N6B3@SDIP56 [DX0056]
ST7FMC2N6B6@SDIP56 [DX0056]
ST7FMC2N6BC@SDIP56 [DX0056]
ST7FMC2N7B3@SDIP56 [DX0056]
ST7FMC2N7B6@SDIP56 [DX0056]
ST7FMC2N7BC@SDIP56 [DX0056]
ST7FMC2R6T3@TQFP64 [DX3012]

ST7FMC2R6T6@TQFP64 [DX3012]
ST7FMC2R6TC@TQFP64 [DX3012]
ST7FMC2R7T3@TQFP64 [DX3012]
ST7FMC2R7T6@TQFP64 [DX3012]
ST7FMC2R7TC@TQFP64 [DX3012]
ST7FMC2S4T3@TQFP44 [DX3003]
ST7FMC2S4T6@TQFP44 [DX3003]
ST7FMC2S4TC@TQFP44 [DX3003]
ST7FMC2S5T3@TQFP44 [DX3003]
ST7FMC2S5T6@TQFP44 [DX3003]
ST7FMC2S5TC@TQFP44 [DX3003]
ST7FMC2S6T3@TQFP44 [DX3003]
ST7FMC2S6T6@TQFP44 [DX3003]
ST7FMC2S6TC@TQFP44 [DX3003]
ST7FMC2S7T3@TQFP44 [DX3003]
ST7FMC2S7T6@TQFP44 [DX3003]
ST7FMC2S7TC@TQFP44 [DX3003]
ST7FOXF1B6 [DX0001]
ST7FOXF1M6 [DX1033]
ST7FOXF2B6 [DX0001]
ST7FOXF2M6 [DX1033]
ST7FOXK1B6 [DX0032]
ST7FOXK1T6 [DX3001]
ST7FOXK2B6 [DX0032]
ST7FOXK2T6 [DX3001]
ST7FSCR1E4M1@SOIC24 [DX1033]
ST7FSCR1R4T1@TQFP64 [DX3016]
STM32F030C6@LQFP48 [DX3007]
STM32F030C8@LQFP48 [DX3007]
STM32F030CC@LQFP48 [DX3007]
STM32F030F4@TSSOP20 [DX1000]
STM32F030K6@LQFP32 [DX3001]
STM32F030R8@LQFP64 [DX3011]
STM32F030RC@LQFP64 [DX3011]
STM32F031C4@LQFP48 [DX3007]
STM32F031C6@LQFP48 [DX3007]
STM32F031F4@TSSOP20 [DX1000]
STM32F031F6@TSSOP20 [DX1000]
STM32F031G4@QFN28 [DX4083]
STM32F031G6@QFN28 [DX4083]
STM32F031K4@QFN32 [DX4015]
STM32F031K6@LQFP32 [DX3001]
STM32F031K6@QFN32 [DX4015]
STM32F038C6@LQFP48 [DX3007]
STM32F038F6@TSSOP20 [DX1000]
STM32F038G6@QFN28 [DX4083]
STM32F038K6@QFN32 [DX4015]
STM32F042C4@LQFP48 [DX3007]
STM32F042C6@LQFP48 [DX3007]
STM32F042C6@QFN48 [DX4021]
STM32F042F4@TSSOP20 [DX1000]
STM32F042F6@TSSOP20 [DX1000]
STM32F042G4@QFN28 [DX4083]
STM32F042G6@QFN28 [DX4083]
STM32F042K4@QFN32 [DX4015]
STM32F042K6@LQFP32 [DX3001]
STM32F042K6@QFN32 [DX4015]
STM32F042T6@WLCSP36 [DX5XXX]
STM32F048C6@LQFP48 [DX3007]
STM32F048C6@QFN48 [DX4021]
STM32F048G6@QFN28 [DX4083]
STM32F048T6@WLCSP36 [DX5XXX]
STM32F050C4@LQFP48 [DX3007]
STM32F050C6@LQFP48 [DX3007]
STM32F050F4@TSSOP20 [DX1000]
STM32F050F6@TSSOP20 [DX1000]
STM32F050G4@QFN28 [DX4083]
STM32F050G6@QFN28 [DX4083]
STM32F050K4@QFN32 [DX4015]
STM32F050K6@LQFP32 [DX3001]
STM32F050K6@QFN32 [DX4015]
STM32F051C4@LQFP48 [DX3007]
STM32F051C6@LQFP48 [DX3007]
STM32F051C6@QFN48 [DX4021]
STM32F051C8@LQFP48 [DX3007]
STM32F051C8@QFN48 [DX4021]
STM32F051K4@LQFP32 [DX3001]
STM32F051K4@QFN32 [DX4015]
STM32F051K6@LQFP32 [DX3001]
STM32F051K6@QFN32 [DX4015]
STM32F051K8@LQFP32 [DX3001]
STM32F051K8@QFN32 [DX4015]
STM32F051R4@LQFP64 [DX3011]
STM32F051R6@LQFP64 [DX3011]
STM32F051R8@LQFP64 [DX3011]
STM32F058C8@QFN48 [DX4021]
STM32F058R8@LQFP64 [DX3011]
STM32F070C6@LQFP48 [DX3007]
STM32F070CB@LQFP48 [DX3007]
STM32F070F6@TSSOP20 [DX1000]
STM32F070RB@LQFP64 [DX3011]
STM32F071CB@LQFP48 [DX3007]
STM32F071CB@QFN48 [DX4021]
STM32F071CB@WLCSP49 [DX5XXX]
STM32F071RB@LQFP64 [DX3011]
STM32F071V8@BGA100 [DX5150]

STM32F071V8@LQFP100 [DX3043]
STM32F071VB@LQFP100 [DX3043]
STM32F072C8@LQFP48 [DX3007]
STM32F072CB@LQFP48 [DX3007]
STM32F072CB@WLCSP49 [DX5XXX]
STM32F072RB@LQFP64 [DX3011]
STM32F072V8@LQFP100 [DX3043]
STM32F072VB@LQFP100 [DX3043]
STM32F078CB@QFN48 [DX4021]
STM32F078RB@LQFP64 [DX3011]
STM32F078VB@LQFP100 [DX3043]
STM32F091CB@QFN48 [DX4021]
STM32F091CC@QFN48 [DX4021]
STM32F091RC@LQFP64 [DX3011]
STM32F091VB@LQFP100 [DX3043]
STM32F091VC@LQFP100 [DX3043]
STM32F100C4@LQFP48(ISP) [DX0001]
STM32F100C6@LQFP48(ISP) [DX0001]
STM32F100C8@LQFP48(ISP) [DX0001]
STM32F100CB@LQFP48(ISP) [DX0001]
STM32F100R4@BGA64(ISP) [DX0001]
STM32F100R4@LQFP64(ISP) [DX0001]
STM32F100R6@BGA64(ISP) [DX0001]
STM32F100R6@LQFP64(ISP) [DX0001]
STM32F100R8@BGA64(ISP) [DX0001]
STM32F100R8@LQFP64(ISP) [DX0001]
STM32F100RB@BGA64(ISP) [DX0001]
STM32F100RB@LQFP64(ISP) [DX0001]
STM32F100RC@LQFP64(ISP) [DX0001]
STM32F100RD@LQFP64(ISP) [DX0001]
STM32F100RE@LQFP64(ISP) [DX0001]
STM32F100V8@LQFP100(ISP) [DX0001]
STM32F100VB@LQFP100 [DX3043]
STM32F100VB@LQFP100(ISP) [DX0001]
STM32F100VC@LQFP100 [DX3043]
STM32F100VC@LQFP100(ISP) [DX0001]
STM32F100VD@LQFP100 [DX3043]
STM32F100VD@LQFP100(ISP) [DX0001]
STM32F100VE@LQFP100 [DX3043]
STM32F100VE@LQFP100(ISP) [DX0001]
STM32F100ZC@LQFP144 [DX3035]
STM32F100ZC@LQFP144(ISP) [DX0001]
STM32F100ZD@LQFP144 [DX3035]
STM32F100ZD@LQFP144(ISP) [DX0001]
STM32F100ZE@LQFP144 [DX3035]
STM32F100ZE@LQFP144(ISP) [DX0001]
STM32F101C4@LQFP48 [DX3007]
STM32F101C4@LQFP48(UART) [DX3007]
STM32F071VB@BGA100 [DX5150]
STM32F072C6@QFN48 [DX4021]
STM32F072C8@QFN48 [DX4021]
STM32F072CB@QFN48 [DX4021]
STM32F072R8@LQFP64 [DX3011]
STM32F072V8@BGA100 [DX5150]
STM32F072VB@BGA100 [DX5150]
STM32F078CB@LQFP48 [DX3007]
STM32F078CB@WLCSP49 [DX5XXX]
STM32F078VB@BGA100 [DX5150]
STM32F091CB@LQFP48 [DX3007]
STM32F091CC@LQFP48 [DX3007]
STM32F091RB@LQFP64 [DX3011]
STM32F091VB@BGA100 [DX5150]
STM32F091VC@BGA100 [DX5150]
STM32F100C4@LQFP48 [DX3007]
STM32F100C6@LQFP48 [DX3007]
STM32F100C8@LQFP48 [DX3007]
STM32F100CB@LQFP48 [DX3007]
STM32F100R4@BGA64 [DX5141]
STM32F100R4@LQFP64 [DX3011]
STM32F100R6@BGA64 [DX5141]
STM32F100R6@LQFP64 [DX3011]
STM32F100R8@BGA64 [DX5141]
STM32F100R8@LQFP64 [DX3011]
STM32F100RB@BGA64 [DX5141]
STM32F100RB@LQFP64 [DX3011]
STM32F100RC@LQFP64 [DX3011]
STM32F100RD@LQFP64 [DX3011]
STM32F100RE@LQFP64 [DX3011]
STM32F100V8@LQFP100 [DX3043]

STM32F101C4@QFN48 [DX4021]
STM32F101C6@LQFP48 [DX3007]
STM32F101C6@LQFP48(UART) [DX3007]
STM32F101C6@QFN48 [DX4021]
STM32F101C8@LQFP48 [DX3007]
STM32F101C8@LQFP48(UART) [DX3007]
STM32F101C8@QFN48 [DX4021]
STM32F101CB@LQFP48 [DX3007]
STM32F101CB@LQFP48(UART) [DX3007]
STM32F101CB@QFN48 [DX4021]
STM32F101R4@LQFP64 [DX3011]
STM32F101R4@LQFP64(UART) [DX3011]
STM32F101R6@LQFP64 [DX3011]
STM32F101R6@LQFP64(UART) [DX3011]
STM32F101R8@LQFP64 [DX3011]
STM32F101R8@LQFP64(UART) [DX3011]
STM32F101RB@LQFP64 [DX3011]
STM32F101RB@LQFP64(UART) [DX3011]
STM32F101RC@LQFP64 [DX3011]
STM32F101RC@LQFP64(UART) [DX3011]
STM32F101RD@LQFP64 [DX3011]
STM32F101RD@LQFP64(UART) [DX3011]
STM32F101RE@LQFP64 [DX3011]
STM32F101RE@LQFP64(UART) [DX3011]
STM32F101RF@LQFP64 [DX3011]
STM32F101RG@LQFP64 [DX3011]
STM32F101T4@QFN36 [DX4029]
STM32F101T4@QFN36(UART) [DX4029]
STM32F101T6@QFN36 [DX4029]
STM32F101T6@QFN36(UART) [DX4029]
STM32F101T8@QFN36 [DX4029]
STM32F101T8@QFN36(UART) [DX4029]
STM32F101TB@QFN36 [DX4029]
STM32F101V8@LQFP100 [DX3043]
STM32F101V8@LQFP100(UART) [DX3043]
STM32F101VB@LQFP100 [DX3043]
STM32F101VB@LQFP100(UART) [DX3043]
STM32F101VC@LQFP100 [DX3043]
STM32F101VC@LQFP100(UART) [DX3043]
STM32F101VD@LQFP100 [DX3043]
STM32F101VD@LQFP100(UART) [DX3043]
STM32F101VE@LQFP100 [DX3043]
STM32F101VE@LQFP100(UART) [DX3043]
STM32F101VF@LQFP100 [DX3043]
STM32F101VG@LQFP100 [DX3043]
STM32F101ZC@LQFP144 [DX3035]
STM32F101ZC@LQFP144(UART) [DX3035]
STM32F101ZD@LQFP144 [DX3035]
STM32F101ZD@LQFP144(UART) [DX3035]
STM32F101ZE@LQFP144 [DX3035]
STM32F101ZE@LQFP144(UART) [DX3035]
STM32F101ZF@LQFP144 [DX3035]
STM32F101ZG@LQFP144 [DX3035]
STM32F102C4@LQFP48 [DX3007]
STM32F102C4@LQFP48(UART) [DX3007]
STM32F102C6@LQFP48 [DX3007]
STM32F102C6@LQFP48(UART) [DX3007]
STM32F102C8@LQFP48 [DX3007]
STM32F102C8@LQFP48(UART) [DX3007]

STM32F102CB@LQFP48 [DX3007]
STM32F102CB@LQFP48(UART) [DX3007]
STM32F102R4@LQFP64 [DX3011]
STM32F102R4@LQFP64(UART) [DX3011]
STM32F102R6@LQFP64 [DX3011]
STM32F102R6@LQFP64(UART) [DX3011]
STM32F102R8@LQFP64 [DX3011]
STM32F102R8@LQFP64(UART) [DX3011]
STM32F102RB@LQFP64 [DX3011]
STM32F102RB@LQFP64(UART) [DX3011]
STM32F103C4@LQFP48 [DX3007]
STM32F103C4@LQFP48(UART) [DX3007]
STM32F103C4@QFN48 [DX4021]
STM32F103C6@LQFP48 [DX3007]
STM32F103C6@LQFP48(UART) [DX3007]
STM32F103C6@QFN48 [DX4021]
STM32F103C8@LQFP48 [DX3007]
STM32F103C8@LQFP48(UART) [DX3007]
STM32F103C8@QFN48 [DX4021]
STM32F103CB@LQFP48 [DX3007]
STM32F103CB@LQFP48(UART) [DX3007]
STM32F103CB@QFN48 [DX4021]
STM32F103R4@FBGA64 [DX5141]
STM32F103R4@LQFP64 [DX3011]
STM32F103R4@LQFP64(UART) [DX3011]
STM32F103R6@FBGA64 [DX5141]
STM32F103R6@LQFP64 [DX3011]
STM32F103R6@LQFP64(UART) [DX3011]
STM32F103R8@FBGA64 [DX5141]
STM32F103R8@LQFP64 [DX3011]
STM32F103R8@LQFP64(UART) [DX3011]
STM32F103RB@FBGA64 [DX5141]
STM32F103RB@LQFP64 [DX3011]
STM32F103RB@LQFP64(UART) [DX3011]
STM32F103RC@LQFP64 [DX3011]
STM32F103RC@LQFP64(UART) [DX3011]
STM32F103RC@WLCSP64 [DX5193]
STM32F103RD@LQFP64 [DX3011]
STM32F103RD@LQFP64(UART) [DX3011]
STM32F103RD@WLCSP64 [DX5193]
STM32F103RE@LQFP64 [DX3011]
STM32F103RE@LQFP64(UART) [DX3011]
STM32F103RE@WLCSP64 [DX5193]
STM32F103RF@LQFP64 [DX3011]
STM32F103RG@LQFP64 [DX3011]
STM32F103T4@QFN36 [DX4029]
STM32F103T4@QFN36(UART) [DX4029]
STM32F103T6@QFN36 [DX4029]
STM32F103T6@QFN36(UART) [DX4029]
STM32F103T8@QFN36 [DX4029]
STM32F103T8@QFN36(UART) [DX4029]
STM32F103TB@QFN36 [DX4029]
STM32F103V8@BGA100 [DX5106]
STM32F103V8@BGA100(UART) [DX5106]
STM32F103V8@LQFP100 [DX3043]
STM32F103V8@LQFP100(UART) [DX3043]
STM32F103VB@BGA100 [DX5106]
STM32F103VB@BGA100(UART) [DX5106]
STM32F103VB@LQFP100 [DX3043]
STM32F103VB@LQFP100(UART) [DX3043]
STM32F103VB@UFBGA100 [DX5150]
STM32F103VC@BGA100 [DX5106]
STM32F103VC@BGA100(UART) [DX5106]

STM32F103VC@LQFP100 [DX3043]
STM32F103VC@LQFP100(UART) [DX3043]
STM32F103VD@BGA100 [DX5106]
STM32F103VD@BGA100(UART) [DX5106]
STM32F103VD@LQFP100 [DX3043]
STM32F103VD@LQFP100(UART) [DX3043]
STM32F103VE@BGA100 [DX5106]
STM32F103VE@BGA100(UART) [DX5106]
STM32F103VE@LQFP100 [DX3043]
STM32F103VE@LQFP100(UART) [DX3043]
STM32F103VF@LQFP100 [DX3043]
STM32F103VG@LQFP100 [DX3043]
STM32F103ZC@BGA144 [DX5107]
STM32F103ZC@BGA144(UART) [DX5107]
STM32F103ZC@LQFP144 [DX3035]
STM32F103ZC@LQFP144(UART) [DX3035]
STM32F103ZD@BGA144 [DX5107]
STM32F103ZD@BGA144(UART) [DX5107]
STM32F103ZD@LQFP144 [DX3035]
STM32F103ZD@LQFP144(UART) [DX3035]
STM32F103ZE@BGA144 [DX5107]
STM32F103ZE@BGA144(UART) [DX5107]
STM32F103ZE@LQFP144 [DX3035]
STM32F103ZE@LQFP144(UART) [DX3035]
STM32F103ZF@BGA144 [DX5107]
STM32F103ZF@LQFP144 [DX3035]
STM32F103ZG@BGA144 [DX5107]
STM32F103ZG@LQFP144 [DX3035]
STM32F105R8@LQFP64 [DX3011]
STM32F105RB@LQFP64 [DX3011]
STM32F105RC@LQFP64 [DX3011]
STM32F105V8@LQFP100 [DX3043]
STM32F105VB@BGA100 [DX5106]
STM32F105VB@LQFP100 [DX3043]
STM32F105VC@BGA100 [DX5106]
STM32F105VC@LQFP100 [DX3043]
STM32F107RB@LQFP64 [DX3011]
STM32F107RC@LQFP64 [DX3011]
STM32F107VB@LQFP100 [DX3043]
STM32F107VC@LQFP100 [DX3043]
STM32F205RB@LQFP64 [DX3011]
STM32F205RC@LQFP64 [DX3011]
STM32F205RE@LQFP64 [DX3011]
STM32F205RE@WLCSP66 [DX5240]
STM32F205RF@LQFP64 [DX3011]
STM32F205RG@LQFP64 [DX3011]
STM32F205RG@WLCSP66 [DX5240]
STM32F205VB@LQFP100 [DX3043]
STM32F205VC@LQFP100 [DX3043]
STM32F205VE@LQFP100 [DX3043]
STM32F205VF@LQFP100 [DX3043]
STM32F205VG@LQFP100 [DX3043]
STM32F205ZC@LQFP144 [DX3051]
STM32F205ZE@LQFP144 [DX3051]
STM32F205ZF@LQFP144 [DX3051]
STM32F205ZG@LQFP144 [DX3051]
STM32F207IC@LQFP176 [DX3135]
STM32F207IC@UFBGA176 [DX5231]
STM32F207IE@LQFP176 [DX3135]
STM32F207IE@UFBGA176 [DX5231]
STM32F207IF@LQFP176 [DX3135]
STM32F207IF@UFBGA176 [DX5231]
STM32F207IG@LQFP176 [DX3135]
STM32F207IG@UFBGA176 [DX5231]
STM32F207VC@LQFP100 [DX3043]
STM32F207VE@LQFP100 [DX3043]
STM32F207VF@LQFP100 [DX3043]
STM32F207VG@LQFP100 [DX3043]
STM32F207ZC@LQFP144 [DX3051]
STM32F207ZE@LQFP144 [DX3051]
STM32F207ZF@LQFP144 [DX3051]
STM32F207ZG@LQFP144 [DX3051]
STM32F215RE@LQFP64 [DX3011]
STM32F215RG@LQFP64 [DX3011]

STM32F215VE@LQFP100 [DX3043]
STM32F215VG@LQFP100 [DX3043]
STM32F215ZE@LQFP144 [DX3051]
STM32F215ZG@LQFP144 [DX3051]
STM32F217IE@LQFP176 [DX3135]
STM32F217IE@UFBGA176 [DX5231]
STM32F217IG@LQFP176 [DX3135]
STM32F217IG@UFBGA176 [DX5231]
STM32F217VE@LQFP100 [DX3043]
STM32F217VG@LQFP100 [DX3043]
STM32F217ZE@LQFP144 [DX3051]
STM32F217ZG@LQFP144 [DX3051]
STM32F301C6@LQFP48 [DX3007]
STM32F301C8@LQFP48 [DX3007]
STM32F301K6@QFN32 [DX4015]
STM32F301K8@QFN32 [DX4015]
STM32F301R6@LQFP64 [DX3011]
STM32F301R8@LQFP64 [DX3011]
STM32F301VB@LQFP100 [DX3043]
STM32F301VC@LQFP100 [DX3043]
STM32F302C6@LQFP48 [DX3007]
STM32F302C8@LQFP48 [DX3007]
STM32F302CB@LQFP48 [DX3007]
STM32F302CC@LQFP48 [DX3007]
STM32F302K6@QFN32 [DX4015]
STM32F302K8@QFN32 [DX4015]
STM32F302R6@LQFP64 [DX3011]
STM32F302R8@LQFP64 [DX3011]
STM32F302RB@LQFP64 [DX3011]
STM32F302RC@LQFP64 [DX3011]
STM32F302RD@LQFP64 [DX3011]
STM32F302RE@LQFP64 [DX3011]
STM32F302VB@LQFP100 [DX3043]
STM32F302VC@LQFP100 [DX3043]
STM32F302VD@BGA100 [DX5150]
STM32F302VD@LQFP100 [DX3043]
STM32F302VE@BGA100 [DX5150]
STM32F302VE@LQFP100 [DX3043]
STM32F302ZD@LQFP144 [DX3035]
STM32F302ZE@LQFP144 [DX3035]
STM32F303C6@LQFP48 [DX3007]
STM32F303C8@LQFP48 [DX3007]
STM32F303CB@LQFP48 [DX3007]
STM32F303CC@LQFP48 [DX3007]
STM32F303K6@N32 [DX4015]
STM32F303K8@N32 [DX4015]
STM32F303R6@LQ64 [DX3011]
STM32F303R8@LQ64 [DX3011]
STM32F303RB@LQFP64 [DX3011]
STM32F303RC@LQFP64 [DX3011]
STM32F303RD@LQ64 [DX3011]
STM32F303RE@LQ64 [DX3011]
STM32F303VB@LQFP100 [DX3043]
STM32F303VC@LQFP100 [DX3043]
STM32F303VD@B100 [DX5150]
STM32F303VD@L100 [DX3043]
STM32F303VE@B100 [DX5150]
STM32F303VE@L100 [DX3043]
STM32F303ZD@Q144 [DX3035]
STM32F303ZE@Q144 [DX3035]
STM32F313CB@LQ48 [DX3007]
STM32F313CC@LQ48 [DX3007]
STM32F313RB@LQ64 [DX3011]
STM32F313RC@LQ64 [DX3011]
STM32F313VB@L100 [DX3043]
STM32F313VC@L100 [DX3043]
STM32F318K8@N32 [DX4015]
STM32F328C8@LQ48 [DX3007]
STM32F334C4@LQ48 [DX3007]
STM32F334C6@LQ48 [DX3007]
STM32F334C8@LQ48 [DX3007]
STM32F334K4@LQ32 [DX3001]
STM32F334K6@LQ32 [DX3001]
STM32F334K8@LQ32 [DX3001]
STM32F334R4@LQ64 [DX3011]
STM32F334R6@LQ64 [DX3011]
STM32F334R8@LQ64 [DX3011]
STM32F358CC@LQ48 [DX3007]
STM32F358RC@LQ64 [DX3011]
STM32F358VC@L100 [DX3043]
STM32F372C8@LQFP48 [DX3007]
STM32F372CB@LQFP48 [DX3007]
STM32F372CC@LQFP48 [DX3007]
STM32F372R8@LQFP64 [DX3011]
STM32F372RB@LQFP64 [DX3011]
STM32F372RC@LQFP64 [DX3011]
STM32F372V8@LQFP100 [DX3043]
STM32F372VB@LQFP100 [DX3043]
STM32F372VC@B100 [DX5150]
STM32F372VC@LQFP100 [DX3043]
STM32F373C8@LQFP48 [DX3007]
STM32F373CB@LQFP48 [DX3007]
STM32F373CC@LQFP48 [DX3007]
STM32F373R8@LQFP64 [DX3011]
STM32F373RB@LQFP64 [DX3011]
STM32F373RC@LQFP64 [DX3011]

STM32F373V8@LQFP100 [DX3043]
STM32F373VB@LQFP100 [DX3043]
STM32F373VC@B100 [DX5150]
STM32F378CC@LQ48 [DX3007]
STM32F378RC@LQ64 [DX3011]
STM32F378VC@L100 [DX3043]
STM32F382C8@LQ48 [DX3007]
STM32F382CB@LQ48 [DX3007]
STM32F382CC@LQ48 [DX3007]
STM32F382R8@LQ64 [DX3011]
STM32F382RB@LQ64 [DX3011]
STM32F382RC@LQ64 [DX3011]
STM32F382V8@L100 [DX3043]
STM32F382VB@L100 [DX3043]
STM32F382VC@B100 [DX5150]
STM32F382VC@L100 [DX3043]
STM32F383C8@LQ48 [DX3007]
STM32F383CB@LQ48 [DX3007]
STM32F383CC@LQ48 [DX3007]
STM32F383R8@LQ64 [DX3011]
STM32F383RB@LQ64 [DX3011]
STM32F383RC@LQ64 [DX3011]
STM32F383V8@L100 [DX3043]
STM32F383VB@L100 [DX3043]
STM32F383VC@B100 [DX5150]
STM32F383VC@L100 [DX3043]
STM32F398VE@L100 [DX3043]
STM32F401CB@QFN48 [DX4021]
STM32F401CB@WLCSP49 [DX5261]
STM32F401CC@QFN48 [DX4021]
STM32F401CC@WLCSP49 [DX5261]
STM32F401CD@QFN48 [DX4021]
STM32F401CD@WLCSP49 [DX5261]
STM32F401CE@QFN48 [DX4021]
STM32F401CE@WLCSP49 [DX5261]
STM32F401RB@LQFP64 [DX3011]
STM32F401RC@LQFP64 [DX3011]
STM32F401RD@LQFP64 [DX3011]
STM32F401RE@LQFP64 [DX3011]
STM32F401VB@FBGA100 [DX5150]
STM32F401VB@LQFP100 [DX3043]
STM32F401VC@FBGA100 [DX5150]
STM32F401VC@LQFP100 [DX3043]
STM32F401VD@FBGA100 [DX5150]
STM32F401VD@LQFP100 [DX3043]
STM32F401VE@FBGA100 [DX5150]
STM32F401VE@LQFP100 [DX3043]
STM32F405RG@LQFP64 [DX3011]
STM32F405VG@LQFP100 [DX3043]
STM32F405ZG@LQFP144 [DX3051]
STM32F407IE@LQFP176 [DX3135]
STM32F407IE@UFBGA176 [DX5260]
STM32F407IG@LQFP176 [DX3135]
STM32F407IG@UFBGA176 [DX5260]
STM32F407VE@LQFP100 [DX3043]
STM32F407VG@LQFP100 [DX3043]
STM32F407ZE@LQFP144 [DX3051]
STM32F407ZG@LQFP144 [DX3051]
STM32F411CC@QFN48 [DX4021]
STM32F411CC@WCLSP49 [DX5261]
STM32F411CE@QFN48 [DX4021]
STM32F411CE@WCLSP49 [DX5261]
STM32F411RC@LQFP64 [DX3011]
STM32F411RE@LQFP64 [DX3011]
STM32F411VC@BGA100 [DX5150]
STM32F411VC@LQFP100 [DX3043]
STM32F411VE@BGA100 [DX5150]
STM32F411VE@LQFP100 [DX3043]
STM32F415RG@LQFP64 [DX3011]
STM32F415VG@LQFP100 [DX3043]
STM32F415ZG@LQFP144 [DX3051]
STM32F417IE@LQFP176 [DX3135]
STM32F417IE@UFBGA176 [DX5260]
STM32F417IG@LQFP176 [DX3135]
STM32F417IG@UFBGA176 [DX5260]
STM32F417VE@LQFP100 [DX3043]
STM32F417VG@LQFP100 [DX3043]
STM32F417ZE@LQFP144 [DX3051]
STM32F417ZG@LQFP144 [DX3051]
STM32F427IG@BGA176 [DX5260]
STM32F427IG@LQFP176 [DX3135]
STM32F427II@BGA176 [DX5260]
STM32F427II@LQFP176 [DX3135]
STM32F427VG@LQFP100 [DX3043]
STM32F427VI@LQFP100 [DX3043]
STM32F427ZG@LQFP144 [DX3051]
STM32F427ZI@LQFP144 [DX3051]
STM32F429IE@BGA176 [DX5260]
STM32F429IE@LQFP176 [DX3135]
STM32F429IG@BGA176 [DX5260]
STM32F429IG@LQFP176 [DX3135]
STM32F429II@BGA176 [DX5260]
STM32F429II@LQFP176 [DX3135]
STM32F429VE@LQFP100 [DX3043]
STM32F429VG@LQFP100 [DX3043]
STM32F429VI@LQFP100 [DX3043]

STM32F429ZE@LQFP144 [DX3051]
STM32F429ZG@LQFP144 [DX3051]
STM32F429ZI@LQFP144 [DX3051]
STM32F437IG@BGA176 [DX5260]
STM32F437IG@LQFP176 [DX3135]
STM32F437II@BGA176 [DX5260]
STM32F437II@LQFP176 [DX3135]
STM32F437VG@LQFP100 [DX3043]
STM32F437VI@LQFP100 [DX3043]
STM32F437ZG@LQFP144 [DX3051]
STM32F437ZI@LQFP144 [DX3051]
STM32F439IG@BGA176 [DX5260]
STM32F439IG@LQFP176 [DX3135]
STM32F439II@BGA176 [DX5260]
STM32F439II@LQFP176 [DX3135]
STM32F439VG@LQFP100 [DX3043]
STM32F439VI@LQFP100 [DX3043]
STM32F439ZG@LQFP144 [DX3051]
STM32F439ZI@LQFP144 [DX3051]
STM32F446RC@LQFP64 [DX3011]
STM32F446RE@LQFP64 [DX3011]
STM32F446VC@LQFP100 [DX3043]
STM32F446VE@LQFP100 [DX3043]
STM32F446ZC@LQFP144 [DX3051]
STM32F446ZE@LQFP144 [DX3051]
STM32FEBKC6@LQFP48 [DX3007]
STM32L051C6@LQFP48 [DX3007]
STM32L051C8@LQFP48 [DX3007]
STM32L051K6@LQFP32 [DX3001]
STM32L051K6@QFN32 [DX4015]
STM32L051K8@LQFP32 [DX3001]
STM32L051K8@QFN32 [DX4015]
STM32L051R6@LQFP64 [DX3011]
STM32L051R8@LQFP64 [DX3011]
STM32L052C6@LQFP48 [DX3007]
STM32L052C8@LQFP48 [DX3007]
STM32L052K6@LQFP32 [DX3001]
STM32L052K6@QFN32 [DX4015]
STM32L052K8@LQFP32 [DX3001]
STM32L052K8@QFN32 [DX4015]
STM32L052R6@LQFP64 [DX3011]
STM32L052R8@LQFP64 [DX3011]
STM32L053C6@LQFP48 [DX3007]
STM32L053C8@LQFP48 [DX3007]
STM32L053R6@LQFP64 [DX3011]
STM32L053R8@LQFP64 [DX3011]
STM32L063C8@LQFP48 [DX3007]
STM32L063R8@LQFP64 [DX3011]
STM32L073CB@LQFP48 [DX3007]
STM32L073CZ@LQFP48 [DX3007]
STM32L073RB@BGA64 [DX5141]
STM32L073RB@LQFP64 [DX3011]
STM32L073RZ@BGA64 [DX5141]
STM32L073RZ@LQFP64 [DX3011]
STM32L073V8@BGA100 [DX5150]
STM32L073V8@LQFP100 [DX3043]
STM32L073VB@BGA100 [DX5150]
STM32L073VB@LQFP100 [DX3043]
STM32L073VZ@BGA100 [DX5150]
STM32L073VZ@LQFP100 [DX3043]
STM32L100C6@QFN48 [DX4021]
STM32L100R8@LQFP64 [DX3011]
STM32L100RB@LQFP64 [DX3011]
STM32L100RC@LQFP64 [DX3011]
STM32L151C6@LQFP48 [DX3007]
STM32L151C6@QFN48 [DX4021]
STM32L151C8@LQFP48 [DX3007]
STM32L151C8@QFN48 [DX4021]
STM32L151CB@LQFP48 [DX3007]
STM32L151CB@QFN48 [DX4021]
STM32L151CC@LQFP48 [DX3007]
STM32L151CC@QFN48 [DX4021]
STM32L151QC@BGA132 [DX5150]
STM32L151QD@BGA132 [DX5150]
STM32L151QE@BGA132 [DX5150]
STM32L151R6@BGA64 [DX5141]
STM32L151R6@LQFP64 [DX3011]
STM32L151R8@BGA64 [DX5141]
STM32L151R8@LQFP64 [DX3011]
STM32L151RB@BGA64 [DX5141]
STM32L151RB@LQFP64 [DX3011]
STM32L151RC@LQFP64 [DX3011]
STM32L151RD@LQFP64 [DX3011]
STM32L151RE@LQFP64 [DX3011]
STM32L151V8@BGA100 [DX5150]
STM32L151V8@LQFP100 [DX3043]
STM32L151VB@BGA100 [DX5150]
STM32L151VB@LQFP100 [DX3043]
STM32L151VC@BGA100 [DX5150]
STM32L151VC@LQFP100 [DX3043]
STM32L151VD@LQFP100 [DX3043]
STM32L151VE@LQFP100 [DX3043]
STM32L151ZC@LQFP144 [DX3035]
STM32L151ZD@LQFP144 [DX3035]
STM32L151ZE@LQFP144 [DX3035]
STM32L152C6@LQFP48 [DX3007]

STM32L152C6@QFN48 [DX4021]
STM32L152C8@QFN48 [DX4021]
STM32L152CB@QFN48 [DX4021]
STM32L152CC@QFN48 [DX4021]
STM32L152QD@BGA132 [DX5150]
STM32L152R6@BGA64 [DX5141]
STM32L152R8@BGA64 [DX5141]
STM32L152RB@BGA64 [DX5141]
STM32L152RC@LQFP64 [DX3011]
STM32L152RE@LQFP64 [DX3011]
STM32L152V8@LQFP100 [DX3043]
STM32L152VB@LQFP100 [DX3043]
STM32L152VC@LQFP100 [DX3043]
STM32L152VE@LQFP100 [DX3043]
STM32L152ZD@LQFP144 [DX3035]
STM32L162QD@BGA132 [DX5150]
STM32L162RD@LQFP64 [DX3011]
STM32L162VC@BGA100 [DX5150]
STM32L162VD@LQFP100 [DX3043]
STM32L162ZD@LQFP144 [DX3035]
STM32W108C8@QFN48 [DX4021]
STM32W108CC@QFN48 [DX4021]
STM32W108HB@QFN40 [DX4017]
STM8AF5166@LQFP32 [DX3001-1]
STM8AF5169@LQFP64 [DX3011-1]
STM8AF5178@LQFP48 [DX3007-1]
STM8AF5186@LQFP32 [DX3001-1]
STM8AF5189@LQFP64 [DX3011-1]
STM8AF5198@LQFP48 [DX3007-1]
STM8AF519A@LQFP80 [DX3017-1]
STM8AF51A9@LQFP64 [DX3011-1]
STM8AF5268@LQFP48 [DX3007-1]
STM8AF5288@LQFP48 [DX3007-1]
STM8AF528A@LQFP80 [DX3017-1]
STM8AF52A9@LQFP64 [DX3011-1]
STM8AF6126@LQFP32 [DX3001-1]
STM8AF6148@LQFP48 [DX3007-1]
STM8AF6168@LQFP48 [DX3007-1]
STM8AF6176@LQFP32 [DX3001-1]
STM8AF6179@LQFP64 [DX3011-1]
STM8AF6188@LQFP48 [DX3007-1]
STM8AF618A@LQFP80 [DX3017-1]
STM8AF6199@LQFP64 [DX3011-1]
STM8AF61A8@LQFP48 [DX3007-1]
STM8AF61AA@LQFP80 [DX3017-1]
STM8AF6246@LQFP32 [DX3001-1]
STM8AF6248@LQFP48 [DX3007-1]
STM8AF6266@QFN32 [DX4015-1]
STM32L152C8@LQFP48 [DX3007]
STM32L152CB@LQFP48 [DX3007]
STM32L152CC@LQFP48 [DX3007]
STM32L152QC@BGA132 [DX5150]
STM32L152QE@BGA132 [DX5150]
STM32L152R6@LQFP64 [DX3011]
STM32L152R8@LQFP64 [DX3011]
STM32L152RB@LQFP64 [DX3011]
STM32L152RD@LQFP64 [DX3011]
STM32L152V8@BGA100 [DX5150]
STM32L152VB@BGA100 [DX5150]
STM32L152VC@BGA100 [DX5150]
STM32L152VD@LQFP100 [DX3043]
STM32L152ZC@LQFP144 [DX3035]
STM32L152ZE@LQFP144 [DX3035]
STM32L162RC@LQFP64 [DX3011]
STM32L162RE@LQFP64 [DX3011]
STM32L162VC@LQFP100 [DX3043]
STM32L162VE@LQFP100 [DX3043]
STM32L162ZE@LQFP144 [DX3035]
STM32W108CB@QFN48 [DX4021]
STM32W108CZ@QFN48 [DX4021]
STM33F372VC@LQFP100 [DX3043]
STM8AF5168@LQFP48 [DX3007-1]
STM8AF5176@LQFP32 [DX3001-1]
STM8AF5179@LQFP64 [DX3011-1]
STM8AF5188@LQFP48 [DX3007-1]
STM8AF518A@LQFP80 [DX3017-1]
STM8AF5199@LQFP64 [DX3011-1]
STM8AF51A8@LQFP48 [DX3007-1]
STM8AF51AA@LQFP80 [DX3017-1]
STM8AF5269@LQFP64 [DX3011-1]
STM8AF5289@LQFP64 [DX3011-1]
STM8AF52A8@LQFP48 [DX3007-1]
STM8AF52AA@LQFP80 [DX3017-1]
STM8AF6146@LQFP32 [DX3001-1]
STM8AF6166@LQFP32 [DX3001-1]
STM8AF6169@LQFP64 [DX3011-1]
STM8AF6178@LQFP48 [DX3007-1]
STM8AF6186@LQFP32 [DX3001-1]
STM8AF6189@LQFP64 [DX3011-1]
STM8AF6198@LQFP48 [DX3007-1]
STM8AF619A@LQFP80 [DX3017-1]
STM8AF61A9@LQFP64 [DX3011-1]
STM8AF6226@LQFP32 [DX3001-1]
STM8AF6246@QFN32 [DX4015-1]
STM8AF6266@LQFP32 [DX3001-1]
STM8AF6268@LQFP48 [DX3007-1]

STM8AF6269@LQFP64 [DX3011-1]
STM8AF6286@LQFP32 [DX3001-1]
STM8AF6288@LQFP48 [DX3007-1]
STM8AF6289@LQFP64 [DX3011-1]
STM8AF628A@LQFP80 [DX3017-1]
STM8AF62A8@LQFP48 [DX3007-1]
STM8AF62A9@LQFP64 [DX3011-1]
STM8AF62AA@LQFP80 [DX3017-1]
STM8AH5166@QFP32 [DX3001-1]
STM8AH5168@QFP48 [DX3007-1]
STM8AH5169@QFP64 [DX3011-1]
STM8AH5176@QFP32 [DX3001-1]
STM8AH5178@QFP48 [DX3007-1]
STM8AH5179@QFP64 [DX3011-1]
STM8AH5186@QFP32 [DX3001-1]
STM8AH5188@QFP48 [DX3007-1]
STM8AH5189@QFP64 [DX3011-1]
STM8AH518A@LQFP80 [DX3017-1]
STM8AH5198@QFP48 [DX3007-1]
STM8AH5199@QFP64 [DX3011-1]
STM8AH519A@LQFP80 [DX3017-1]
STM8AH51A8@QFP48 [DX3007-1]
STM8AH51A9@QFP64 [DX3011-1]
STM8AH51AA@LQFP80 [DX3017-1]
STM8AH5268@LQFP48 [DX3007-1]
STM8AH5269@LQFP64 [DX3011-1]
STM8AH5288@LQFP48 [DX3007-1]
STM8AH5289@LQFP64 [DX3011-1]
STM8AH528A@LQFP80 [DX3017-1]
STM8AH52A8@LQFP48 [DX3007-1]
STM8AH52A9@LQFP64 [DX3011-1]
STM8AH52AA@LQFP80 [DX3017-1]
STM8AH6126@LQFP32 [DX3001-1]
STM8AH6146@LQFP32 [DX3001-1]
STM8AH6148@LQFP48 [DX3007-1]
STM8AH6166@LQFP32 [DX3001-1]
STM8AH6168@LQFP48 [DX3007-1]
STM8AH6169@LQFP64 [DX3011-1]
STM8AH6176@LQFP32 [DX3001-1]
STM8AH6178@LQFP48 [DX3007-1]
STM8AH6179@LQFP64 [DX3011-1]
STM8AH6186@LQFP32 [DX3001-1]
STM8AH6188@LQFP48 [DX3007-1]
STM8AH6189@LQFP64 [DX3011-1]
STM8AH618A@LQFP80 [DX3017-1]
STM8AH6198@LQFP48 [DX3007-1]
STM8AH6199@LQFP64 [DX3011-1]
STM8AH619A@LQFP80 [DX3017-1]
STM8AH61A8@LQFP48 [DX3007-1]
STM8AH61A9@LQFP64 [DX3011-1]
STM8AH61AA@LQFP80 [DX3017-1]
STM8AH6226@LQFP32 [DX3001-1]
STM8AH6246@LQFP32 [DX3001-1]
STM8AH6246@QFN32 [DX4015-1]
STM8AH6248@LQFP48 [DX3007-1]
STM8AH6266@LQFP32 [DX3001-1]
STM8AH6266@QFN32 [DX4015-1]
STM8AH6268@LQFP48 [DX3007-1]
STM8AH6269@LQFP64 [DX3011-1]
STM8AH6286@LQFP32 [DX3001-1]
STM8AH6288@LQFP48 [DX3007-1]
STM8AH6289@LQFP64 [DX3011-1]
STM8AH628A@LQFP80 [DX3017-1]
STM8AH62A8@LQFP48 [DX3007-1]
STM8AH62A9@LQFP64 [DX3011-1]
STM8AH62AA@LQFP80 [DX3017-1]
STM8AudioH66@LQFP32 [DX3001-1]
STM8AudioH78@LQFP48 [DX3007-1]
STM8AudioHAA@LQFP80 [DX3017-1]
STM8L051F3@TSSOP20 [DX1067-2]
STM8L052C6@LQFP48 [DX3007-3]
STM8L052R8@LQFP64 [DX3011-4]
STM8L101F1@QFN20 [DX4041-2]
STM8L101F1@TSSOP20 [DX1067-2]
STM8L101F2@QFN20 [DX4041-2]
STM8L101F2@TSSOP20 [DX1067-2]
STM8L101F3@QFN20 [DX4041-2]
STM8L101F3@TSSOP20 [DX1067-2]
STM8L101G2@QFN28 [DX4083-2]
STM8L101G3@QFN28 [DX4083-2]
STM8L101K3@LQFP32 [DX3001-2]
STM8L101K3@QFN32 [DX4015-2]
STM8L151C2@LQFP48 [DX3007-3]
STM8L151C3@LQFP48 [DX3007-3]
STM8L151C4@LQFP48 [DX3007-3]
STM8L151C4@QFN48 [DX4021-1]
STM8L151C6@LQFP48 [DX3007-3]
STM8L151C6@QFN48 [DX4021-1]
STM8L151C8@LQFP48 [DX3007-3]
STM8L151C8@QFN48 [DX4021-1]
STM8L151F2@QFN20 [DX4041-2]
STM8L151F2@TSSOP20 [DX1067-2]
STM8L151F3@QFN20 [DX4041-2]
STM8L151F3@TSSOP20 [DX1067-2]
STM8L151G2@QFN28 [DX4083-2]
STM8L151G3@QFN28 [DX4083-2]

STM8L151G4@QFN28 [DX4083-2]	STM8L151G6@QFN28 [DX4083-2]
STM8L151K2@QFN32 [DX4015-2]	STM8L151K3@QFN32 [DX4015-2]
STM8L151K4@LQFP32 [DX3001-2]	STM8L151K4@QFN32 [DX4015-2]
STM8L151K6@LQFP32 [DX3001-2]	STM8L151K6@QFN32 [DX4015-2]
STM8L151M8@LQFP80 [DX3017-2]	STM8L151R6@LQFP64 [DX3011-4]
STM8L151R8@LQFP64 [DX3011-4]	STM8L152C4@LQFP48 [DX3007-3]
STM8L152C4@QFN48 [DX4021-1]	STM8L152C6@LQFP48 [DX3007-3]
STM8L152C6@QFN48 [DX4021-1]	STM8L152C8@LQFP48 [DX3007-3]
STM8L152C8@QFN48 [DX4021-1]	STM8L152K4@LQFP32 [DX3001-2]
STM8L152K4@QFN32 [DX4015-2]	STM8L152K6@LQFP32 [DX3001-2]
STM8L152K6@QFN32 [DX4015-2]	STM8L152M8@LQFP80 [DX3017-2]
STM8L152R6@LQFP64 [DX3011-4]	STM8L152R8@LQFP64 [DX3011-4]
STM8S003F3@QFN20 [DX4041-1]	STM8S003F3@TSSOP20 [DX1067-1]
STM8S003K3@LQFP32 [DX3001-1]	STM8S005C6@LQFP48 [DX3007-1]
STM8S005K6@LQFP32 [DX3001-1]	STM8S007C8@QFP48 [DX3007-1]
STM8S103F2@QFN20 [DX4041-1]	STM8S103F2@SOP20 [DX1033-3]
STM8S103F2@TSSOP20 [DX1067-1]	STM8S103F3@QFN20 [DX4041-1]
STM8S103F3@SOP20 [DX1033-3]	STM8S103F3@TSSOP20 [DX1067-1]
STM8S103K2@SDIP32 [DX0032-1]	STM8S103K3@LQFP32 [DX3001-1]
STM8S103K3@QFN32 [DX4015-1]	STM8S103K3@SDIP32 [DX0032-1]
STM8S105C4@LQFP48 [DX3007-1]	STM8S105C6@LQFP48 [DX3007-1]
STM8S105K4@LQFP32 [DX3001-1]	STM8S105K4@QFN32 [DX4015-1]
STM8S105K4@SDIP32 [DX0032-1]	STM8S105K6@LQFP32 [DX3001-1]
STM8S105K6@QFN32 [DX4015-1]	STM8S105K6@SDIP32 [DX0032-1]
STM8S105S4@LQFP44 [DX3005-1]	STM8S105S6@LQFP44 [DX3005-1]
STM8S207C6@LQFP48 [DX3007-1]	STM8S207C8@LQFP48 [DX3007-1]
STM8S207CB@LQFP48 [DX3007-1]	STM8S207K6@LQFP32 [DX3001-1]
STM8S207M8@LQFP80 [DX3017-1]	STM8S207MB@LQFP80 [DX3017-1]
STM8S207R6@LQFP64[10*10] [DX3011-1]	
STM8S207R6@LQFP64[14*14] [DX3044-1]	
STM8S207R8@LQFP64[10*10] [DX3011-1]	
STM8S207R8@LQFP64[14*14] [DX3044-1]	
STM8S207RB@LQFP64[10*10] [DX3011-1]	
STM8S207RB@LQFP64[14*14] [DX3044-1]	
STM8S207S6@LQFP44 [DX3005-1]	STM8S207S8@LQFP44 [DX3005-1]
STM8S207SB@LQFP44 [DX3005-1]	STM8S208C6@LQFP48 [DX3007-1]
STM8S208C8@LQFP48 [DX3007-1]	STM8S208CB@LQFP48 [DX3007-1]
STM8S208MB@LQFP80 [DX3017-1]	
STM8S208R6@LQFP64[10*10] [DX3011-1]	
STM8S208R6@LQFP64[14*14] [DX3044-1]	
STM8S208R8@LQFP64[10*10] [DX3011-1]	
STM8S208R8@LQFP64[14*14] [DX3044-1]	
STM8S208RB@LQFP64[10*10] [DX3011-1]	
STM8S208RB@LQFP64[14*14] [DX3044-1]	
STM8S208S6@LQFP44 [DX3005-1]	STM8S208S8@LQFP44 [DX3005-1]
STM8S208SB@LQFP44 [DX3005-1]	STM8S903F3@SOP20 [DX1033-3]
STM8S903F3@TSSOP20 [DX1067-1]	STM8S903K3@LQFP32 [DX3001-1]
STM8S903K3@QFN32 [DX4015-1]	STM8S903K3@SDIP32 [DX0032-1]

STM8TL52F4@TSSOP20 [DX1067-4]
STM8TL52G4@QFN28 [DX4083-3]
STM8TL53C4@QFN48 [DX4021-2]
STM8TL53F4@TSSOP20 [DX1067-4]
STM8TL53G4@QFN28 [DX4083-3]
STR711FR0T6@LQFP64 [DX3011]
STR711FR0T7@LQFP64 [DX3011]
STR711FR1T6@LQFP64 [DX3011]
STR711FR1T7@LQFP64 [DX3011]
STR711FR2T6@LQFP64 [DX3011]
STR711FR2T7@LQFP64 [DX3011]
STR711FZ0T6@LQFP144 [DX3035]
STR711FZ0T7@LQFP144 [DX3035]
STR711FZ1T6@LQFP144 [DX3035]
STR711FZ1T7@LQFP144 [DX3035]
STR711FZ2T6@LQFP144 [DX3035]
STR711FZ2T7@LQFP144 [DX3035]
STR712FR0T6@LQFP64 [DX3011]
STR712FR0T7@LQFP64 [DX3011]
STR712FR1T6@LQFP64 [DX3011]
STR712FR1T7@LQFP64 [DX3011]
STR712FR2T6@LQFP64 [DX3011]
STR712FR2T7@LQFP64 [DX3011]
STR712FZ0T6@LQFP144 [DX3035]
STR712FZ0T7@LQFP144 [DX3035]
STR712FZ1T6@LQFP144 [DX3035]
STR712FZ1T7@LQFP144 [DX3035]
STR712FZ2T6@LQFP144 [DX3035]
STR712FZ2T7@LQFP144 [DX3035]
STR715FR0T6@LQFP64 [DX3011]
STR715FR0T7@LQFP64 [DX3011]
STR715FR1T6@LQFP64 [DX3011]
STR715FR1T7@LQFP64 [DX3011]
STR715FR2T6@LQFP64 [DX3011]
STR715FR2T7@LQFP64 [DX3011]
STR715FZ0T6@LQFP144 [DX3035]
STR715FZ0T7@LQFP144 [DX3035]
STR715FZ1T6@LQFP144 [DX3035]
STR715FZ1T7@LQFP144 [DX3035]
STR715FZ2T6@LQFP144 [DX3035]
STR715FZ2T7@LQFP144 [DX3035]
STR750FR0T6@LQFP64 [DX3011]
STR750FR0T7@LQFP64 [DX3011]
STR750FR1T6@LQFP64 [DX3011]
STR750FR1T7@LQFP64 [DX3011]
STR750FR2T6@LQFP64 [DX3011]
STR750FR2T7@LQFP64 [DX3011]
STR750FV0T6@LQFP100 [DX3021]
STR750FV0T7@LQFP100 [DX3021]
STR750FV1T6@LQFP100 [DX3021]
STR750FV1T7@LQFP100 [DX3021]
STR750FV2T6@LQFP100 [DX3021]
STR750FV2T7@LQFP100 [DX3021]
STR751FR0T6@LQFP64 [DX3011]
STR751FR0T7@LQFP64 [DX3011]
STR751FR1T6@LQFP64 [DX3011]
STR751FR1T7@LQFP64 [DX3011]
STR751FR2T6@LQFP64 [DX3011]
STR751FR2T7@LQFP64 [DX3011]
STR751FV0T6@LQFP100 [DX3021]
STR751FV0T7@LQFP100 [DX3021]
STR751FV1T6@LQFP100 [DX3021]
STR751FV1T7@LQFP100 [DX3021]
STR751FV2T6@LQFP100 [DX3021]
STR751FV2T7@LQFP100 [DX3021]
STR752FR0T6@LQFP64 [DX3011]
STR752FR0T7@LQFP64 [DX3011]
STR752FR1T6@LQFP64 [DX3011]
STR752FR1T7@LQFP64 [DX3011]
STR752FR2T6@LQFP64 [DX3011]
STR752FR2T7@LQFP64 [DX3011]
STR752FV0T6@LQFP100 [DX3021]
STR752FV0T7@LQFP100 [DX3021]
STR752FV1T6@LQFP100 [DX3021]
STR752FV1T7@LQFP100 [DX3021]
STR752FV2T6@LQFP100 [DX3021]
STR752FV2T7@LQFP100 [DX3021]
STR755FR0T6@LQFP64 [DX3011]
STR755FR0T7@LQFP64 [DX3011]
STR755FR1T6@LQFP64 [DX3011]
STR755FR1T7@LQFP64 [DX3011]
STR755FR2T6@LQFP64 [DX3011]
STR755FR2T7@LQFP64 [DX3011]
STR755FV0T6@LQFP100 [DX3021]
STR755FV0T7@LQFP100 [DX3021]
STR755FV1T6@LQFP100 [DX3021]
STR755FV1T7@LQFP100 [DX3021]
STR755FV2T6@LQFP100 [DX3021]
STR755FV2T7@LQFP100 [DX3021]
STR910FAM32@LQFP80 [DX3016]
STR910FAM32@LQFP80(ISP) [DX0001]
STR910FAW32@LQFP128 [DX3030]
STR910FAW32@LQFP128(ISP) [DX0001]
STR910FAZ32@LFBGA144 [DX5107]

STR910FAZ32@LFBGA144(ISP) [DX0001]
STR910FM32@LQFP80 [DX3016]
STR910FM32@LQFP80(ISP) [DX0001]
STR910FW32@LQFP128 [DX3030]
STR910FW32@LQFP128(ISP) [DX0001]
STR911FAM42@LQFP80 [DX3016]
STR911FAM42@LQFP80(ISP) [DX0001]
STR911FAM44@LQFP80 [DX3016]
STR911FAM44@LQFP80(ISP) [DX0001]
STR911FAM46@LQFP80 [DX3016]
STR911FAM46@LQFP80(ISP) [DX0001]
STR911FAM47@LQFP80 [DX3016]
STR911FAM47@LQFP80(ISP) [DX0001]
STR911FAW42@LQFP128 [DX3030]
STR911FAW42@LQFP128(ISP) [DX0001]
STR911FAW44@LQFP128 [DX3030]
STR911FAW44@LQFP128(ISP) [DX0001]
STR911FAW46@LQFP128 [DX3030]
STR911FAW46@LQFP128(ISP) [DX0001]
STR911FAW47@LQFP128 [DX3030]
STR911FAW47@LQFP128(ISP) [DX0001]
STR911FM42@LQFP80 [DX3016]
STR911FM42@LQFP80(ISP) [DX0001]
STR911FM44@LQFP80 [DX3016]
STR911FM44@LQFP80(ISP) [DX0001]
STR912FAW32@LQFP128 [DX3030]
STR912FAW32@LQFP128(ISP) [DX0001]
STR912FAW42@LQFP128 [DX3030]
STR912FAW42@LQFP128(ISP) [DX0001]
STR912FAW44@LQFP128 [DX3030]
STR912FAW44@LQFP128(ISP) [DX0001]
STR912FAW46@LQFP128 [DX3030]
STR912FAW46@LQFP128(ISP) [DX0001]
STR912FAW47@LQFP128 [DX3030]
STR912FAW47@LQFP128(ISP) [DX0001]
STR912FAZ42@LFBGA144 [DX5107]
STR912FAZ42@LFBGA144(ISP) [DX0001]
STR912FAZ44@LFBGA144 [DX5107]
STR912FAZ44@LFBGA144(ISP) [DX0001]
STR912FAZ46@LFBGA144 [DX5107]
STR912FAZ46@LFBGA144(ISP) [DX0001]
STR912FAZ47@LFBGA144 [DX5107]
STR912FAZ47@LFBGA144(ISP) [DX0001]
STR912FW42@LQFP128 [DX3030]
STR912FW42@LQFP128(ISP) [DX0001]
STR912FW44@LQFP128 [DX3030]
STR912FW44@LQFP128(ISP) [DX0001]
uPSD3212A@TQFP52 [DX3010]
uPSD3212A@TQFP52(new) [DX3010]
uPSD3212A@TQFP80 [DX3016]
uPSD3212A@TQFP80(new) [DX3016]
uPSD3212AV@TQFP52 [DX3010]
uPSD3212AV@TQFP52(new) [DX3010]
uPSD3212AV@TQFP80 [DX3016]
uPSD3212AV@TQFP80(new) [DX3016]
uPSD3212B@TQFP52 [DX3010]
uPSD3212B@TQFP80 [DX3016]
uPSD3212BV@TQFP52 [DX3010]
uPSD3212BV@TQFP80 [DX3016]
uPSD3212C@TQFP52 [DX3010]
uPSD3212C@TQFP80 [DX3016]
uPSD3212CV@TQFP52 [DX3010]
uPSD3212CV@TQFP80 [DX3016]
uPSD3233B@TQFP52 [DX3010]
uPSD3233B@TQFP80 [DX3016]
uPSD3233BV@TQFP52 [DX3010]
uPSD3233BV@TQFP80 [DX3016]
uPSD3234A@TQFP52 [DX3010]
uPSD3234A@TQFP80 [DX3016]

uPSD3234BV@TQFP52 [DX3010]	uPSD3234BV@TQFP80 [DX3016]
uPSD3253B@TQFP52 [DX3010]	uPSD3253B@TQFP80 [DX3016]
uPSD3253BV@TQFP52 [DX3010]	uPSD3253BV@TQFP80 [DX3016]
uPSD3254A(new)@TQFP52 [DX3009]	uPSD3254A(new)@TQFP80 [DX3016]
uPSD3254A@TQFP52 [DX3010]	uPSD3254A@TQFP80 [DX3016]
uPSD3254BV(new)@TQFP52 [DX3009]	uPSD3254BV(new)@TQFP80 [DX3016]
uPSD3254BV@TQFP52 [DX3010]	uPSD3254BV@TQFP80 [DX3016]
uUPSD3334D@TQFP52 [DX3009]	uUPSD3334D@TQFP80 [DX3016]
uUPSD3334DB@TQFP52 [DX3009]	uUPSD3334DB@TQFP80 [DX3016]
uUPSD3334DV@TQFP52 [DX3009]	uUPSD3334DV@TQFP80 [DX3016]
uUPSD3334DVB@TQFP52 [DX3009]	uUPSD3334DVB@TQFP80 [DX3016]
uUPSD3354D@TQFP52 [DX3009]	uUPSD3354D@TQFP80 [DX3016]
uUPSD3354DB@TQFP52 [DX3009]	uUPSD3354DB@TQFP80 [DX3016]
uUPSD3354DV@TQFP52 [DX3009]	uUPSD3354DV@TQFP80 [DX3016]
uUPSD3354DVB@TQFP52 [DX3009]	uUPSD3354DVB@TQFP80 [DX3016]
uUPSD3434E(new)@TQFP52 [DX3010]	uUPSD3434E(new)@TQFP80 [DX3016]
uUPSD3434E@TQFP52 [DX3010]	uUPSD3434E@TQFP80 [DX3016]
uUPSD3434EB(new)@TQFP52 [DX3010]	uUPSD3434EB(new)@TQFP80 [DX3016]
uUPSD3434EB@TQFP52 [DX3010]	uUPSD3434EB@TQFP80 [DX3016]
uUPSD3434EV(new)@TQFP52 [DX3010]	uUPSD3434EV(new)@TQFP80 [DX3016]
uUPSD3434EV@TQFP52 [DX3010]	uUPSD3434EV@TQFP80 [DX3016]
uUPSD3434EVB(new)@TQFP52 [DX3010]	
uUPSD3434EVB(new)@TQFP80 [DX3016]	
uUPSD3434EVB@TQFP52 [DX3010]	uUPSD3434EVB@TQFP80 [DX3016]
uUPSD3454E(new)@TQFP52 [DX3010]	uUPSD3454E(new)@TQFP80 [DX3016]
uUPSD3454E@TQFP52 [DX3010]	uUPSD3454E@TQFP80 [DX3016]
uUPSD3454EB(new)@TQFP52 [DX3010]	uUPSD3454EB(new)@TQFP80 [DX3016]
uUPSD3454EB@TQFP52 [DX3010]	uUPSD3454EB@TQFP80 [DX3016]
uUPSD3454EV(new)@TQFP52 [DX3010]	uUPSD3454EV(new)@TQFP80 [DX3016]
uUPSD3454EV@TQFP52 [DX3010]	uUPSD3454EV@TQFP80 [DX3016]
uUPSD3454EVB(new)@TQFP52 [DX3010]	
uUPSD3454EVB(new)@TQFP80 [DX3016]	
uUPSD3454EVB@TQFP52 [DX3010]	uUPSD3454EVB@TQFP80 [DX3016]
ZPSD211R@PLCC44 [DX2044]	ZPSD211R@TQFP44 [DX3003]
ZPSD211RV@PLCC44 [DX2044]	ZPSD211RV@TQFP44 [DX3003]
ZPSD301@PLCC44 [DX2044]	ZPSD301@TQFP44 [DX3003]
ZPSD301L@PLCC44 [DX2044]	ZPSD301L@TQFP44 [DX3003]
ZPSD301R@PLCC44 [DX2044]	ZPSD301R@TQFP44 [DX3003]
ZPSD301RL@PLCC44 [DX2044]	ZPSD301RL@TQFP44 [DX3003]
ZPSD301RV@PLCC44 [DX2044]	ZPSD301RV@TQFP44 [DX3003]
ZPSD301V@PLCC44 [DX2044]	ZPSD301V@TQFP44 [DX3003]
ZPSD302@PLCC44 [DX2044]	ZPSD302@TQFP44 [DX3003]
ZPSD302B@PLCC44 [DX2044]	ZPSD302B@PLCC44(USA) [DX2044]
ZPSD302L@PLCC44 [DX2044]	ZPSD302L@TQFP44 [DX3003]
ZPSD302R@PLCC44 [DX2044]	ZPSD302R@TQFP44 [DX3003]
ZPSD302RL@PLCC44 [DX2044]	ZPSD302RL@TQFP44 [DX3003]
ZPSD302RV@PLCC44 [DX2044]	ZPSD302RV@TQFP44 [DX3003]
ZPSD302V@PLCC44 [DX2044]	ZPSD302V@TQFP44 [DX3003]

ZPSD303@PLCC44 [DX2044]
ZPSD303L@PLCC44 [DX2044]
ZPSD303R@PLCC44 [DX2044]
ZPSD303RL@PLCC44 [DX2044]
ZPSD303RV@PLCC44 [DX2044]
ZPSD303V@PLCC44 [DX2044]
ZPSD311@PLCC44 [DX2044]
ZPSD311L@PLCC44 [DX2044]
ZPSD311R@PLCC44 [DX2044]
ZPSD311RL@PLCC44 [DX2044]
ZPSD311RV@PLCC44 [DX2044]
ZPSD311V@PLCC44 [DX2044]
ZPSD312@PLCC44 [DX2044]
ZPSD312B@PLCC44 [DX2044]
ZPSD312L@TQFP44 [DX3046]
ZPSD312R@TQFP44 [DX3046]
ZPSD312RL@TQFP44 [DX3046]
ZPSD312RV@TQFP44 [DX3046]
ZPSD312V@TQFP44 [DX3046]
ZPSD313@TQFP44 [DX3003]
ZPSD313L@TQFP44 [DX3003]
ZPSD313R@TQFP44 [DX3003]
ZPSD313RL@TQFP44 [DX3003]
ZPSD313RV@TQFP44 [DX3003]
ZPSD313V@TQFP44 [DX3003]
ZPSD813F4@PLCC52 [DX2052]
ZPSD303@TQFP44 [DX3003]
ZPSD303L@TQFP44 [DX3003]
ZPSD303R@TQFP44 [DX3003]
ZPSD303RL@TQFP44 [DX3003]
ZPSD303RV@TQFP44 [DX3003]
ZPSD303V@TQFP44 [DX3003]
ZPSD311@TQFP44 [DX3003]
ZPSD311L@TQFP44 [DX3003]
ZPSD311R@TQFP44 [DX3003]
ZPSD311RL@TQFP44 [DX3003]
ZPSD311RV@TQFP44 [DX3003]
ZPSD311V@TQFP44 [DX3003]
ZPSD312@TQFP44 [DX3046]
ZPSD312L@PLCC44 [DX2044]
ZPSD312R@PLCC44 [DX2044]
ZPSD312RL@PLCC44 [DX2044]
ZPSD312RV@PLCC44 [DX2044]
ZPSD312V@PLCC44 [DX2044]
ZPSD313@PLCC44 [DX2044]
ZPSD313L@PLCC44 [DX2044]
ZPSD313R@PLCC44 [DX2044]
ZPSD313RL@PLCC44 [DX2044]
ZPSD313RV@PLCC44 [DX2044]
ZPSD313V@PLCC44 [DX2044]
ZPSD813F2@PLCC52 [DX2052]

STC

MICROCONTROLLER

STC89C516RD [DX0001]
STC89C516RD@TQFP44 [DX3003]
STC89C58RD@PLCC44 [DX2044]
STC89LE516AD [DX0001]
STC89LE516AD@TQFP44 [DX3003]
STC89LE516X2@PLCC44 [DX2044]
STC89LE52AD [DX0001]
STC89LE52AD@TQFP44 [DX3003]
STC89LE54AD@PLCC44 [DX2044]
STC89LE556AD [DX0001]
STC89LE556AD@TQFP44 [DX3003]
STC89LE556X2@PLCC44 [DX2044]
STC89LE58AD [DX0001]
STC89LE58AD@TQFP44 [DX3003]
STC89LV516RD@PLCC44 [DX2044]
STC89LV58RD [DX0001]
STC89C516RD@PLCC44 [DX2044]
STC89C58RD [DX0001]
STC89C58RD@TQFP44 [DX3003]
STC89LE516AD@PLCC44 [DX2044]
STC89LE516X2 [DX0001]
STC89LE516X2@TQFP44 [DX3003]
STC89LE52AD@PLCC44 [DX2044]
STC89LE54AD [DX0001]
STC89LE54AD@TQFP44 [DX3003]
STC89LE556AD@PLCC44 [DX2044]
STC89LE556X2 [DX0001]
STC89LE556X2@TQFP44 [DX3003]
STC89LE58AD@PLCC44 [DX2044]
STC89LV516RD [DX0001]
STC89LV516RD@TQFP44 [DX3003]
STC89LV58RD@PLCC44 [DX2044]

STC89LV58RD@TQFP44 [DX3003]

ST-CUSTOMER

E(E)PROM/FRAM/NVRAM

NAND01GR3B2BZA6(HYBM)@FBGA63 [DX5046]
NAND01GR3B2BZA6(HYTY)@FBGA63 [DX5046]
NAND01GR3B2CZA6(ACCTON)@FBGA63 [DX5046]
NAND01GR3B2CZA6(HYBM)@FBGA63 [DX5046]
NAND01GR3B2CZA6(INSPUR)@FBGA63 [DX5046]
NAND01GW3B2BN6(INTEL)@TSOP48 [DX1004]
NAND01GW3B2BN6(LGE03)@TSOP48 [DX1004]
NAND01GW3B2BZA6(ACCTON)@FBGA63 [DX5046]
NAND01GW3B2CN6(BATM)@TSOP48 [DX1004-1]
NAND01GW3B2CN6(ChuangJ)@TSOP48 [DX1004-3]
NAND01GW3B2CN6(INTEL)@TSOP48 [DX1004-1]
NAND01GW3B2CN6(MOTOROLA)@TSOP48 [DX1004-1]
NAND01GW3B2CN6(SKYWORTH)@TSOP48 [DX1004-1]
NAND01GW3B2CN6(ST7161)@TSOP48 [DX1004-1]
NAND01GW3B2CN6@TSOP48(DaXian) [DX1004-1]
NAND01GW3B2CZA6(ACCTON)@FBGA63 [DX5046]
NAND01GW3B2CZA6(JiuZhou)@FBGA63 [DX5046]
NAND01GW3B2CZA6(ST)@FBGA63 [DX5046]
NAND02GW3B2DN6(INSPUR)@TSOP48 [DX1004]
NAND02GW3B2DN6(LGE04)@TSOP48 [DX1004]
NAND02GW3B2DN6(SP)@TSOP48 [DX1004-3]
NAND02GW3B2DN6(UT)@TSOP48 [DX1004]
NAND02GW3B2DN6E(ST7142)@TSOP48 [DX1004]
NAND02GW3B2DZA6(CAL-COMP)@FBGA63 [DX5046]
NAND04GW3B2DN6(BATM)@TSOP48 [DX1004-1]
NAND256W3A2BN6(ZTE)@TSOP48 [DX1004]
NAND256W3A2BZA6(ZTE)@VFBGA55 [DX5005]
NAND512W3A2BZA6(ZTE)@TFBGA63 [DX5046]
NAND512W3A2DN6(CHUANGJIA)@TSOP48 [DX1004]
NAND99R4M2AZBA5(HB)@FBGA149 [DX5013]
NANDA9R3N1CZBC5(XSR1.0)@FBGA137 [DX5011]

MICROCONTROLLER

STM32F103R8@LQFP64 [DX3011]
STM32F207IG@BGA137 [DX5086]

SULC

E(E)PROM/FRAM/NVRAM

CF48F6300M0U0BE [DX0051]
CF48F6300M0U0BE(SPEC) [DX0051]
CF48F6600M0U0BE [DX0051]
CF48F6600M0U0BE(SPEC) [DX0051]
CF48F6600M0U0SF [DX0051]
CF48F6600M0U0SF(1G) [DX0051]
PF48F6600M0U0SE [DX0051]
PF48F6600M0U0SE(1G) [DX0051]
RD48F4000L0ZBQ0 [DX0051]
RD48F4000L0ZBQ1 [DX0051]
RD48F4400L0ZDN0 [DX0051]
RD48F4400L0ZDN2 [DX0051]

SUMMIT

E(E)PROM/FRAM/NVRAM

S24022 [DX0001]
S24022@SOIC8 [DX1045]
S24023 [DX0001]
S24023@SOIC8 [DX1045]
S24042 [DX0001]
S24042@SOIC8 [DX1045]
S24043 [DX0001]
S24043@SOIC8 [DX1045]
S24162 [DX0001]
S24162@SOIC8 [DX1045]
S24VP02 [DX0001]
S24VP02@SOIC8 [DX1045]
S24VP04 [DX0001]
S24VP04@SOIC8 [DX1045]
S24VP08 [DX0001]
S24VP08@SOIC8 [DX1045]
S24VP16 [DX0001]
S24VP16@SOIC8 [DX1045]
S93462(08bit) [DX0001]
S93462(08bit)@SOIC8 [DX1045]
S93462(16bit) [DX0001]
S93462(16bit)@SOIC8 [DX1045]
S93463(08bit) [DX0001]
S93463(08bit)@SOIC8 [DX1045]
S93463(16bit) [DX0001]
S93463(16bit)@SOIC8 [DX1045]
S93662(08bit) [DX0001]
S93662(08bit)@SOIC8 [DX1045]
S93662(16bit) [DX0001]
S93662(16bit)@SOIC8 [DX1045]
S93663(08bit) [DX0001]
S93663(08bit)@SOIC8 [DX1045]
S93663(16bit) [DX0001]
S93663(16bit)@SOIC8 [DX1045]
S93WD462(08bit) [DX0001]
S93WD462(08bit)@SOIC8 [DX1045]
S93WD462(16bit) [DX0001]
S93WD462(16bit)@SOIC8 [DX1045]
S93WD463(08bit) [DX0001]
S93WD463(08bit)@SOIC8 [DX1045]
S93WD463(16bit) [DX0001]
S93WD463(16bit)@SOIC8 [DX1045]
S93WD662(08bit) [DX0001]
S93WD662(08bit)@SOIC8 [DX1045]
S93WD662(16bit) [DX0001]
S93WD662(16bit)@SOIC8 [DX1045]
S93WD663(08bit) [DX0001]
S93WD663(08bit)@SOIC8 [DX1045]
S93WD663(16bit) [DX0001]
S93WD663(16bit)@SOIC8 [DX1045]

MICROCONTROLLER

SMM465F-249@TQFP48 [DX3007]
SMM465F-249@TQFP48(ISP) [DX0001]
SMM665BFC-266@TQFP48 [DX3007]
SMM665BFC-266@TQFP48(ISP) [DX0001]
SMM665CFC-802@TQFP48(ISP) [DX0001]
SMM665CFC-8022@TQFP48 [DX3007]
SMM766BF [DX3007]
SMM766F [DX3007]

SUMSUNG

E(E)PROM/FRAM/NVRAM

K5E1G12ACB@BGA133 [DX5104]
KMS5U000KM@BGA153 [DX5104]

SUNMOON

E(E)PROM/FRAM/NVRAM

SM24C02 [DX0001]
SM24C02@SOP8 [DX1045]
SM24C04 [DX0001]
SM24C04@SOP8 [DX1045]
SM24C08 [DX0001]
SM24C08@SOP8 [DX1045]
SM24C16 [DX0001]
SM24C16@SOP8 [DX1045]

SUNPLUS

MICROCONTROLLER

SPMC65P2102A(dip18) [DX0001]
SPMC65P2102A(dip18)(ISP) [DX0001]
SPMC65P2102A@SOP18 [DX1033]
SPMC65P2102A@SOP18(ISP) [DX0001]
SPMC65P2104A(dip18) [DX0001]
SPMC65P2104A(dip18)(ISP) [DX0001]
SPMC65P2104A@SOP18 [DX1033]
SPMC65P2104A@SOP18(ISP) [DX0001]
SPMC65P2202A(dip16) [DX0001]
SPMC65P2202A(dip16)(ISP) [DX0001]
SPMC65P2202A(dip20) [DX0001]
SPMC65P2202A(dip20)(ISP) [DX0001]
SPMC65P2202A@SOP16 [DX1033]
SPMC65P2202A@SOP16(ISP) [DX0001]
SPMC65P2202A@SOP20 [DX1033]
SPMC65P2202A@SOP20(ISP) [DX0001]
SPMC65P2204A(dip16) [DX0001]
SPMC65P2204A(dip16)(ISP) [DX0001]
SPMC65P2204A(dip20) [DX0001]
SPMC65P2204A(dip20)(ISP) [DX0001]
SPMC65P2204A@SOP16 [DX1033]
SPMC65P2204A@SOP16(ISP) [DX0001]
SPMC65P2204A@SOP20 [DX1033]
SPMC65P2204A@SOP20(ISP) [DX0001]
SPMC65P2404A(dip20) [DX0001]
SPMC65P2404A(dip20)(ISP) [DX0001]
SPMC65P2404A(dip28) [DX0001]
SPMC65P2404A(dip28)(ISP) [DX0001]
SPMC65P2404A@SOP20 [DX1033]
SPMC65P2404A@SOP20(ISP) [DX0001]
SPMC65P2404A@SOP28 [DX1033]
SPMC65P2404A@SOP28(ISP) [DX0001]
SPMC65P2408A(dip28) [DX0001]
SPMC65P2408A(dip28)(ISP) [DX0001]

SPMC65P2408A(dip32) [DX0001]
SPMC65P2408A(dip32)(ISP) [DX0001]
SPMC65P2408A@SOP28 [DX1033]
SPMC65P2408A@SOP28(ISP) [DX0001]
SPMC65P2408A@SOP32 [DX1034]
SPMC65P2408A@SOP32(ISP) [DX0001]

SYNAPTICS

MICROCONTROLLER

S2200 [DX4039]
S2202 [DX5229-1]

SYNCMOS

E(E)PROM/FRAM/NVRAM

F29C31004B [DX0001]
F29C31004B@PLCC32 [DX2032]
F29C31004B@TSOP32 [DX1002]
F29C31004T [DX0001]
F29C31004T@PLCC32 [DX2032]
F29C31004T@TSOP32 [DX1002]
F29C51000B [DX0001]
F29C51000B@PLCC32 [DX2032]
F29C51000B@TSOP32 [DX1002]
F29C51000T [DX0001]
F29C51000T@PLCC32 [DX2032]
F29C51000T@TSOP32 [DX1002]
F29C51001B [DX0001]
F29C51001B@PLCC32 [DX2032]
F29C51001B@TSOP32 [DX1002]
F29C51001T [DX0001]
F29C51001T@PLCC32 [DX2032]
F29C51001T@TSOP32 [DX1002]
F29C51002B [DX0001]
F29C51002B@PLCC32 [DX2032]
F29C51002B@TSOP32 [DX1002]
F29C51002T [DX0001]
F29C51002T@PLCC32 [DX2032]
F29C51002T@TSOP32 [DX1002]
F29C51004B [DX0001]
F29C51004B@PLCC32 [DX2032]
F29C51004B@TSOP32 [DX1002]
F29C51004T [DX0001]
F29C51004T@PLCC32 [DX2032]
F29C51004T@TSOP32 [DX1002]
F29LC51000 [DX0001]
F29LC51000@PLCC32 [DX2032]
F29LC51000@TSOP32 [DX1002]
F29LC51001 [DX0001]
F29LC51001@PLCC32 [DX2032]
F29LC51001@TSOP32 [DX1002]
F29LC51002 [DX0001]
F29LC51002@PLCC32 [DX2032]
F29LC51002@TSOP32 [DX1002]
S29C31001B [DX0001]
S29C31001B@PLCC32 [DX2032]
S29C31001B@TSOP32 [DX1002]
S29C31001T [DX0001]
S29C31001T@PLCC32 [DX2032]
S29C31001T@TSOP32 [DX1002]
S29C31002B [DX0001]
S29C31002B@PLCC32 [DX2032]
S29C31002B@TSOP32 [DX1002]
S29C31002T [DX0001]
S29C31002T@PLCC32 [DX2032]
S29C31002T@TSOP32 [DX1002]
S29C31004B [DX0001]
S29C31004B@PLCC32 [DX2032]
S29C31004B@TSOP32 [DX1002]
S29C31004T [DX0001]
S29C31004T@PLCC32 [DX2032]
S29C31004T@TSOP32 [DX1002]
S29C51001B [DX0001]
S29C51001B@PLCC32 [DX2032]
S29C51001B@TSOP32 [DX1002]
S29C51001T [DX0001]
S29C51001T@PLCC32 [DX2032]

S29C51001T@TSOP32 [DX1002]
S29C51002B [DX0001]
S29C51002B@PLCC32 [DX2032]
S29C51002B@TSOP32 [DX1002]
S29C51002T [DX0001]
S29C51002T@PLCC32 [DX2032]
S29C51002T@TSOP32 [DX1002]
S29C51004B [DX0001]
S29C51004B@PLCC32 [DX2032]
S29C51004B@TSOP32 [DX1002]
S29C51004T [DX0001]
S29C51004T@PLCC32 [DX2032]
S29C51004T@TSOP32 [DX1002]

MICROCONTROLLER

MSU1958 [DX0001]
MSU1958@PLCC44 [DX2044]
MSU1958@TQFP44 [DX3002]
MSU2952 [DX0001]
MSU2952@PLCC44 [DX2044]
MSU2952@TQFP44 [DX3002]
MSU2964 [DX0001]
MSU2964@PLCC44 [DX2044]
MSU2964@TQFP44 [DX3002]
OB37R04A1@SOP10 [DX1016]
OB37R04A1@SOP14 [DX1016]
OB37R04A1@SOP16 [DX1016]
OB37R259A@SOP14 [DX1016]
OB37R259A@SOP16 [DX1016]
OB39A08T1@QFP32 [DX3001]
OB39A08T1@SOP16 [DX1016]
OB39A08T1@SOP20 [DX1033]
OB39A08T1@SOP24 [DX1033]
OB39A08T1@SOP28 [DX1033]
OB39A08T2@SOP24 [DX1033]
OB39A08T2@SOP28 [DX1033]
OB39A16D1@QFP48 [DX3007]
OB39A16D2@QFP48 [DX3007]
OB39A16T1@QFP32 [DX3001]
OB39A16T1@SOP16 [DX1016]
OB39A16T1@SOP20 [DX1033]
OB39A16T1@SOP24 [DX1033]
OB39A16T1@SOP28 [DX1033]
SM2958 [DX0001]
SM2958@PLCC44 [DX2044]
SM2958@TQFP44 [DX3002]
SM2965 [DX0001]
SM2965@PLCC44 [DX2044]
SM2965@TQFP44 [DX3002]
SM39A16M1@LQFP32 [DX3001]
SM39A16M1@SOP28 [DX1033]
SM39R02G1@DIP10 [DX0001]
SM39R02G1@DIP14 [DX0001]
SM39R02G1@MSOP10 [DX1051]
SM39R02G1@SOP14 [DX1016]
SM39R04G1@DIP10 [DX0001]
SM39R04G1@DIP14 [DX0001]
SM39R04G1@MSOP10 [DX1051]
SM39R04G1@SOP14 [DX1016]
SM39R05A3@DIP10 [DX0001]
SM39R05A3@DIP14 [DX0001]
SM39R05A3@DIP16 [DX0001]
SM39R05A3@DIP20 [DX0001]
SM39R05A3@SOP10 [DX1051]
SM39R05A3@SOP14 [DX1016]
SM39R05A3@SOP16 [DX1016]
SM39R05A3@SOP20 [DX1033]
SM39R05A3@SSOP20 [DX1025]
SM39R05A5@DIP10 [DX0001]
SM39R05A5@DIP8 [DX0001]
SM39R05A5@SOP10 [DX1051]
SM39R05A5@SOP8 [DX1051]
SM39R08A2(dip16) [DX0001]
SM39R08A2(dip20) [DX0001]
SM39R08A2(dip24) [DX0001]
SM39R08A2(dip28) [DX0001]
SM39R08A2@PLCC28 [DX2028]
SM39R08A2@SOP16 [DX1033]
SM39R08A2@SOP20 [DX1033]
SM39R08A2@SOP24 [DX1033]
SM39R08A2@SOP28 [DX1033]
SM39R08A3@DIP10 [DX0001]
SM39R08A3@DIP14 [DX0001]
SM39R08A3@DIP16 [DX0001]
SM39R08A3@DIP20 [DX0001]
SM39R08A3@SOP10 [DX1051]
SM39R08A3@SOP14 [DX1016]
SM39R08A3@SOP16 [DX1016]
SM39R08A3@SOP20 [DX1033]

SM39R08A3@SSOP20 [DX1025]
SM39R08A5@DIP8 [DX0001]
SM39R08A5@SOP8 [DX1051]
SM39R12A2(dip20) [DX0001]
SM39R12A2(dip28) [DX0001]
SM39R12A2@SOP16 [DX1033]
SM39R12A2@SOP24 [DX1033]
SM39R16A2(dip16) [DX0001]
SM39R16A2(dip24) [DX0001]
SM39R16A2@PLCC28 [DX2028]
SM39R16A2@SOP20 [DX1033]
SM39R16A2@SOP28 [DX1033]
SM39R16A3@DIP14 [DX0001]
SM39R16A3@DIP20 [DX0001]
SM39R16A3@LQFP32 [DX3001]
SM39R16A3@SOP14 [DX1016]
SM39R16A3@SOP20 [DX1033]
SM39R16A3@SSOP20 [DX1025]
SM39R16A6@SOP24 [DX1033]
SM39R2051 [DX0001]
SM39R4051 [DX0001]
SM59064 [DX0001]
SM59064@TQFP44 [DX3002]
SM59128C@PLCC44 [DX2044]
SM59128L [DX0001]
SM59128L@TQFP44 [DX3002]
SM5912C(ISP) [DX0001]
SM5912C@PLCC44(ISP) [DX0001]
SM5912C@TQFP44(ISP) [DX0001]
SM5912L(ISP) [DX0001]
SM5912L@PLCC44(ISP) [DX0001]
SM5912L@TQFP44(ISP) [DX0001]
SM59164@PLCC44 [DX2044]
SM5916C [DX0001]
SM5916C@PLCC44 [DX2044]
SM5916C@TQFP44 [DX3002]
SM5916L [DX0001]
SM5916L@PLCC44 [DX2044]
SM5916L@TQFP44 [DX3002]
SM59264 [DX0001]
SM59264@TQFP44 [DX3002]
SM5952@PLCC44 [DX2044]
SM5952EW [DX0001]
SM5952EW@TQFP44 [DX3002]
SM5953@PLCC44 [DX2044]
SM5954W [DX0001]
SM5954W@TQFP44 [DX3002]
SM5958W@PLCC44 [DX2044]
SM39R08A5@DIP10 [DX0001]
SM39R08A5@SOP10 [DX1051]
SM39R12A2(dip16) [DX0001]
SM39R12A2(dip24) [DX0001]
SM39R12A2@PLCC28 [DX2028]
SM39R12A2@SOP20 [DX1033]
SM39R12A2@SOP28 [DX1033]
SM39R16A2(dip20) [DX0001]
SM39R16A2(dip28) [DX0001]
SM39R16A2@SOP16 [DX1033]
SM39R16A2@SOP24 [DX1033]
SM39R16A3@DIP10 [DX0001]
SM39R16A3@DIP16 [DX0001]
SM39R16A3@DIP28 [DX0001]
SM39R16A3@SOP10 [DX1051]
SM39R16A3@SOP16 [DX1016]
SM39R16A3@SOP28 [DX1033]
SM39R16A6@LQFP32 [DX3001]
SM39R16A6@SOP28 [DX1033]
SM39R2051@SOP20 [DX1033]
SM39R4051@SOP20 [DX1033]
SM59064@PLCC44 [DX2044]
SM59128C [DX0001]
SM59128C@TQFP44 [DX3002]
SM59128L@PLCC44 [DX2044]
SM5912C [DX0001]
SM5912C@PLCC44 [DX2044]
SM5912C@TQFP44 [DX3002]
SM5912L [DX0001]
SM5912L@PLCC44 [DX2044]
SM5912L@TQFP44 [DX3002]
SM59164 [DX0001]
SM59164@TQFP44 [DX3002]
SM5916C(ISP) [DX0001]
SM5916C@PLCC44(ISP) [DX0001]
SM5916C@TQFP44(ISP) [DX0001]
SM5916L(ISP) [DX0001]
SM5916L@PLCC44(ISP) [DX0001]
SM5916L@TQFP44(ISP) [DX0001]
SM59264@PLCC44 [DX2044]
SM5952 [DX0001]
SM5952@QFP44 [DX3002]
SM5952EW@PLCC44 [DX2044]
SM5953 [DX0001]
SM5953@QFP44 [DX3002]
SM5954W@PLCC44 [DX2044]
SM5958W [DX0001]
SM5958W@QFP44 [DX3002]

SM5964 [DX0001]
SM5964@PLCC44 [DX2044]
SM5964@TQFP44 [DX3002]
SM5964A [DX0001]
SM5964A@PLCC44 [DX2044]
SM5964A@TQFP44 [DX3002]
SM5964AC [DX0001]
SM5964AC@PLCC44 [DX2044]
SM5964AC@TQFP44 [DX3002]
SM5964AL [DX0001]
SM5964AL@PLCC44 [DX2044]
SM5964AL@TQFP44 [DX3002]
SM5964BW [DX0001]
SM5964BW@PLCC44 [DX2044]
SM5964BW@QFP44 [DX3002]
SM5964C [DX0001]
SM5964C@PLCC44 [DX2044]
SM5964C@TQFP44 [DX3002]
SM5964D0 [DX0001]
SM5964D0@PLCC44 [DX2044]
SM5964D0@TQFP44 [DX3002]
SM5964D0A [DX0001]
SM5964D0A@PLCC44 [DX2044]
SM5964D0A@TQFP44 [DX3002]
SM5964D1A [DX0001]
SM5964D1A@PLCC44 [DX2044]
SM5964D1A@TQFP44 [DX3002]
SM59A16U1 [DX0001]
SM59A16U1@LQFP44 [DX3002]
SM59A16U1@LQFP48 [DX3007]
SM59A16U1@LQFP64 [DX3011]
SM59D02G2C [DX0001]
SM59D02G2C(ISP) [DX0001]
SM59D02G2C@PLCC44 [DX2044]
SM59D02G2C@PLCC44(ISP) [DX0001]
SM59D02G2C@TQFP44 [DX3002]
SM59D02G2C@TQFP44(ISP) [DX0001]
SM59D02G2L [DX0001]
SM59D02G2L(ISP) [DX0001]
SM59D02G2L@PLCC44 [DX2044]
SM59D02G2L@PLCC44(ISP) [DX0001]
SM59D02G2L@TQFP44 [DX3002]
SM59D02G2L@TQFP44(ISP) [DX0001]
SM59D03G2C [DX0001]
SM59D03G2C(ISP) [DX0001]
SM59D03G2C@PLCC44 [DX2044]
SM59D03G2C@PLCC44(ISP) [DX0001]
SM59D03G2C@TQFP44 [DX3002]
SM59D03G2C@TQFP44(ISP) [DX0001]
SM59D03G2L [DX0001]
SM59D03G2L(ISP) [DX0001]
SM59D03G2L@PLCC44 [DX2044]
SM59D03G2L@PLCC44(ISP) [DX0001]
SM59D03G2L@TQFP44 [DX3002]
SM59D03G2L@TQFP44(ISP) [DX0001]
SM59D04G2C [DX0001]
SM59D04G2C(ISP) [DX0001]
SM59D04G2C@PLCC44 [DX2044]
SM59D04G2C@PLCC44(ISP) [DX0001]
SM59D04G2C@TQFP44 [DX3002]
SM59D04G2C@TQFP44(ISP) [DX0001]
SM59D04G2L [DX0001]
SM59D04G2L(ISP) [DX0001]
SM59D04G2L@PLCC44 [DX2044]
SM59D04G2L@PLCC44(ISP) [DX0001]
SM59D04G2L@TQFP44 [DX3002]
SM59D04G2L@TQFP44(ISP) [DX0001]
SM59R01G1 [DX0001]
SM59R01G1@PLCC44 [DX2044]
SM59R01G1@TQFP44 [DX3002]
SM59R02A1C [DX0001]
SM59R02A1C@LQFP48 [DX3007]
SM59R02A1C@PLCC44 [DX2044]
SM59R02A1C@QFP44 [DX3002]
SM59R02A1L [DX0001]
SM59R02A1L@LQFP48 [DX3007]
SM59R02A1L@PLCC44 [DX2044]
SM59R02A1L@QFP44 [DX3002]
SM59R02G1 [DX0001]
SM59R02G1@PLCC44 [DX2044]
SM59R02G1@TQFP44 [DX3002]
SM59R03A1C [DX0001]
SM59R03A1C@LQFP48 [DX3007]
SM59R03A1C@PLCC44 [DX2044]
SM59R03A1C@QFP44 [DX3002]
SM59R03A1L [DX0001]
SM59R03A1L@LQFP48 [DX3007]
SM59R03A1L@PLCC44 [DX2044]
SM59R03A1L@QFP44 [DX3002]
SM59R04A1C [DX0001]
SM59R04A1C@LQFP48 [DX3007]
SM59R04A1C@PLCC44 [DX2044]
SM59R04A1C@QFP44 [DX3002]
SM59R04A1L [DX0001]
SM59R04A1L@LQFP48 [DX3007]
SM59R04A1L@PLCC44 [DX2044]

SM59R04A1L@QFP44 [DX3002]
SM59R04A2C@LQFP48 [DX3007]
SM59R04A2C@QFP44 [DX3002]
SM59R04A2L@LQFP48 [DX3007]
SM59R04A2L@QFP44 [DX3002]
SM59R05A3C@LQFP48 [DX3007]
SM59R05A3C@QFP44 [DX3002]
SM59R05A3L@LQFP48 [DX3007]
SM59R05A3L@QFP44 [DX3002]
SM59R05A5C@LQFP48 [DX3007]
SM59R05A5C@QFP44 [DX3002]
SM59R05A5L@LQFP48 [DX3007]
SM59R05A5L@QFP44 [DX3002]
SM59R05G6W@LQFP48 [DX3007]
SM59R05G6W@QFP44 [DX3002]
SM59R08A2@TQFP64 [DX3011]
SM59R09A3C@LQFP48 [DX3007]
SM59R09A3C@QFP44 [DX3002]
SM59R09A3L@LQFP48 [DX3007]
SM59R09A3L@QFP44 [DX3002]
SM59R09A5C@LQFP48 [DX3007]
SM59R09A5C@QFP44 [DX3002]
SM59R09A5L@LQFP48 [DX3007]
SM59R09A5L@QFP44 [DX3002]
SM59R09G6W@LQFP48 [DX3007]
SM59R09G6W@QFP44 [DX3002]
SM59R16A2@TQFP64 [DX3011]
SM59R16A3C@LQFP48 [DX3007]
SM59R16A3C@QFP44 [DX3002]
SM59R16A3L@LQFP48 [DX3007]
SM59R16A3L@QFP44 [DX3002]
SM59R16A5C@LQFP48 [DX3007]
SM59R16A5C@QFP44 [DX3002]
SM59R16A5L@LQFP48 [DX3007]
SM59R16A5L@QFP44 [DX3002]
SM59R16G6W@LQFP48 [DX3007]
SM59R16G6W@QFP44 [DX3002]
SM7908 [DX0001]
SM7908@TQFP44 [DX3002]
SM79108@PLCC44 [DX2044]
SM79164 [DX0001]
SM79164@TQFP44 [DX3002]
SM79164L@PLCC44 [DX2044]
SM79164V [DX0001]
SM79164V@TQFP44 [DX3002]
SM7932@PLCC44 [DX2044]
SM7964 [DX0001]
SM7964@TQFP44 [DX3002]
SM59R04A2C [DX0001]
SM59R04A2C@PLCC44 [DX2044]
SM59R04A2L [DX0001]
SM59R04A2L@PLCC44 [DX2044]
SM59R05A3C [DX0001]
SM59R05A3C@PLCC44 [DX2044]
SM59R05A3L [DX0001]
SM59R05A3L@PLCC44 [DX2044]
SM59R05A5C [DX0001]
SM59R05A5C@PLCC44 [DX2044]
SM59R05A5L [DX0001]
SM59R05A5L@PLCC44 [DX2044]
SM59R05G6W [DX0001]
SM59R05G6W@PLCC44 [DX2044]
SM59R05G6W@TQFP64 [DX3011]
SM59R09A3C [DX0001]
SM59R09A3C@PLCC44 [DX2044]
SM59R09A3L [DX0001]
SM59R09A3L@PLCC44 [DX2044]
SM59R09A5C [DX0001]
SM59R09A5C@PLCC44 [DX2044]
SM59R09A5L [DX0001]
SM59R09A5L@PLCC44 [DX2044]
SM59R09G6W [DX0001]
SM59R09G6W@PLCC44 [DX2044]
SM59R09G6W@TQFP64 [DX3011]
SM59R16A3C [DX0001]
SM59R16A3C@PLCC44 [DX2044]
SM59R16A3L [DX0001]
SM59R16A3L@PLCC44 [DX2044]
SM59R16A5C [DX0001]
SM59R16A5C@PLCC44 [DX2044]
SM59R16A5L [DX0001]
SM59R16A5L@PLCC44 [DX2044]
SM59R16G6W [DX0001]
SM59R16G6W@PLCC44 [DX2044]
SM59R16G6W@TQFP64 [DX3011]
SM7908@PLCC44 [DX2044]
SM79108 [DX0001]
SM79108@TQFP44 [DX3002]
SM79164@PLCC44 [DX2044]
SM79164L [DX0001]
SM79164L@TQFP44 [DX3002]
SM79164V@PLCC44 [DX2044]
SM7932 [DX0001]
SM7932@TQFP44 [DX3002]
SM7964@PLCC44 [DX2044]
SM894051 [DX0001]

SM894051@SOIC20 [DX1031]
SM8951 [DX0001]
SM8951@PLCC44 [DX2044]
SM8951@TQFP44 [DX3002]
SM89516 [DX0001]
SM89516@PLCC44 [DX2044]
SM89516@TQFP44 [DX3002]
SM89516A [DX0001]
SM89516A@PLCC44 [DX2044]
SM89516A@TQFP44 [DX3002]
SM89516AL [DX0001]
SM89516AL@PLCC44 [DX2044]
SM89516AL@TQFP44 [DX3002]
SM89516B [DX0001]
SM89516B@PLCC44 [DX2044]
SM89516B@TQFP44 [DX3002]
SM89516BL [DX0001]
SM89516BL@PLCC44 [DX2044]
SM89516BL@TQFP44 [DX3002]
SM89516BW [DX0001]
SM89516BW@PLCC44 [DX2044]
SM89516BW@QFP44 [DX3002]
SM89516L [DX0001]
SM89516L@PLCC44 [DX2044]
SM89516L@TQFP44 [DX3002]
SM8951A [DX0001]
SM8951A@PLCC44 [DX2044]
SM8951A@TQFP44 [DX3002]
SM8951AL [DX0001]
SM8951AL@PLCC44 [DX2044]
SM8951AL@TQFP44 [DX3002]
SM8951B [DX0001]
SM8951B@PLCC44 [DX2044]
SM8951B@TQFP44 [DX3002]
SM8951BL [DX0001]
SM8951BL@PLCC44 [DX2044]
SM8951BL@TQFP44 [DX3002]
SM8951L [DX0001]
SM8951L@PLCC44 [DX2044]
SM8951L@TQFP44 [DX3002]
SM8952 [DX0001]
SM8952@PLCC44 [DX2044]
SM8952@TQFP44 [DX3002]
SM8952A [DX0001]
SM8952A@PLCC44 [DX2044]
SM8952A@TQFP44 [DX3002]
SM8952AL [DX0001]
SM8952AL@PLCC44 [DX2044]
SM8952AL@TQFP44 [DX3002]
SM8952B [DX0001]
SM8952B@PLCC44 [DX2044]
SM8952B@TQFP44 [DX3002]
SM8952BL [DX0001]
SM8952BL@PLCC44 [DX2044]
SM8952BL@TQFP44 [DX3002]
SM8952BW [DX0001]
SM8952BW@PLCC44 [DX2044]
SM8952BW@QFP44 [DX3002]
SM8952L [DX0001]
SM8952L@PLCC44 [DX2044]
SM8952L@TQFP44 [DX3002]
SM8954 [DX0001]
SM8954@PLCC44 [DX2044]
SM8954@TQFP44 [DX3002]
SM8954A [DX0001]
SM8954A@PLCC44 [DX2044]
SM8954A@TQFP44 [DX3002]
SM8954AL [DX0001]
SM8954AL@PLCC44 [DX2044]
SM8954AL@TQFP44 [DX3002]
SM8954B [DX0001]
SM8954B@PLCC44 [DX2044]
SM8954B@TQFP44 [DX3002]
SM8954BL [DX0001]
SM8954BL@PLCC44 [DX2044]
SM8954BL@TQFP44 [DX3002]
SM8954BW [DX0001]
SM8954BW@PLCC44 [DX2044]
SM8954BW@QFP44 [DX3002]
SM8954L [DX0001]
SM8954L@PLCC44 [DX2044]
SM8954L@TQFP44 [DX3002]
SM8958 [DX0001]
SM8958@PLCC44 [DX2044]
SM8958@TQFP44 [DX3002]
SM8958A [DX0001]
SM8958A@PLCC44 [DX2044]
SM8958A@TQFP44 [DX3002]
SM8958AL [DX0001]
SM8958AL@PLCC44 [DX2044]
SM8958AL@TQFP44 [DX3002]
SM8958B [DX0001]
SM8958B@PLCC44 [DX2044]
SM8958B@TQFP44 [DX3002]
SM8958BL [DX0001]
SM8958BL@PLCC44 [DX2044]

SM8958BL@TQFP44 [DX3002]
SM8958BW [DX0001]
SM8958BW@PLCC44 [DX2044]
SM8958BW@QFP44 [DX3002]
SM8958L [DX0001]
SM8958L@PLCC44 [DX2044]
SM8958L@TQFP44 [DX3002]
SM89S16R1C [DX0001]
SM89S16R1C@PLCC44 [DX2044]
SM89S16R1C@TQFP44 [DX3002]
SM89T04R1C [DX0001]
SM89T04R1C@PLCC44 [DX2044]
SM89T04R1C@TQFP44 [DX3002]
SM89T04R1L [DX0001]
SM89T04R1L@PLCC44 [DX2044]
SM89T04R1L@TQFP44 [DX3002]
SM89T08R1C [DX0001]
SM89T08R1C@PLCC44 [DX2044]
SM89T08R1C@TQFP44 [DX3002]
SM89T08R1L [DX0001]
SM89T08R1L@PLCC44 [DX2044]
SM89T08R1L@TQFP44 [DX3002]
SM89T16R1C [DX0001]
SM89T16R1C@PLCC44 [DX2044]
SM89T16R1C@TQFP44 [DX3002]
SM89T16R1L [DX0001]
SM89T16R1L@PLCC44 [DX2044]
SM89T16R1L@TQFP44 [DX3002]

SYNERTEK

E(E)PROM/FRAM/NVRAM

SY2716 [DX0001]

SYNTEK

MICROCONTROLLER

STK6031@LQFP48 [DX3007]
STK6031@PLCC44 [DX2044]
STK6031@QFP44 [DX3002]
STK6032 [DX0001]
STK6032@LQFP48 [DX3007]
STK6032@PLCC44 [DX2044]
STK6032@QFP44 [DX3002]
STK6033 [DX0001]
STK6033@LQFP48 [DX3007]
STK6033@PLCC44 [DX2044]
STK6033@QFP44 [DX3002]

SZXG

MICROCONTROLLER

MB95F108AHSPFM [DX3012]
MB95F108AHSPFV [DX3011]
MB95F108AHWPFM [DX3012]
MB95F108AHWPFV [DX3011]
MB95F108AJSPFM [DX3012]
MB95F108AJSPFV [DX3012]
MB95F108AJWPFM [DX3012]
MB95F108AJWPFV [DX3012]
MB95F108AKSPFM [DX3012]
MB95F108AKSPFV [DX3011]
MB95F108AKWPFM [DX3012]
MB95F108AKWPFV [DX3011]
MB95F108AMSPFM [DX3012]
MB95F108AMSPFV [DX3011]
MB95F108AMWPFM [DX3012]
MB95F108AMWPFV [DX3011]
MB95F108ANSPFM [DX3012]
MB95F108ANSPFV [DX3012]

MB95F108ANWPFM [DX3012]
MB95F108ATSPFM [DX3012]
MB95F108ATWPFM [DX3012]
MB95F108BHSPFM [DX3012]
MB95F108BHWPFM [DX3012]
MB95F108BJSPFM [DX3012]
MB95F108BJWPFM [DX3012]
MB95F108BKSPFM [DX3012]
MB95F108BKWPFM [DX3012]
MB95F108BMSPFM [DX3012]
MB95F108BMWPFM [DX3012]
MB95F108BNSPFM [DX3012]
MB95F108BNWPFM [DX3012]
MB95F108BTSPFM [DX3012]
MB95F108BTWPFM [DX3012]
MB95F108ANWPFV [DX3012]
MB95F108ATSPFV [DX3011]
MB95F108ATWPFV [DX3011]
MB95F108BHSPFV [DX3011]
MB95F108BHWPFV [DX3011]
MB95F108BJSPFV [DX3012]
MB95F108BJWPFV [DX3012]
MB95F108BKSPFV [DX3011]
MB95F108BKWPFV [DX3011]
MB95F108BMSPFV [DX3011]
MB95F108BMWPFV [DX3011]
MB95F108BNSPFV [DX3012]
MB95F108BNWPFV [DX3012]
MB95F108BTSPFV [DX3011]
MB95F108BTWPFV [DX3011]

TDICOMS

MICROCONTROLLER

TDS33X1@PLCC44 [DX2044]
TDS33X2@PLCC44 [DX2044]
TDS33X4@PLCC44 [DX2044]
TDS33X8@PLCC44 [DX2044]
TDS33X1@TQFP44 [DX3002]
TDS33X2@TQFP44 [DX3002]
TDS33X4@TQFP44 [DX3002]
TDS33X8@TQFP44 [DX3002]

TECHALL

MICROCONTROLLER

MN103SFC2D [DX3003]
MN103SFJ9D [DX3003]
MN103SFC2DXW [DX3003]
MN103SFJ9DXW [DX3003]

TECHCODE

MICROCONTROLLER

T89C516 [DX0001]
T89C516@TQFP44 [DX3002]
T89C52@PLCC44 [DX2044]
T89C58 [DX0001]
T89C58@TQFP44 [DX3002]
T89C516@PLCC44 [DX2044]
T89C52 [DX0001]
T89C52@TQFP44 [DX3002]
T89C58@PLCC44 [DX2044]

TEKMOS

MICROCONTROLLER

TK87C751 [DX0001]
TK87C751@PLCC28 [DX2028]

TELFORD

MICROCONTROLLER

M30280F6HP [DX3016]
M30280F8HP [DX3016]
M30280FAHP [DX3016]
M30280FATHP [DX3016]
M30280FAVHP [DX3016]
M30280FCHP [DX3016]
M30281F6HP [DX3011]
M30281F8HP [DX3011]
M30281FAHP [DX3011]
M30281FATHP [DX3011]
M30281FAVHP [DX3011]
M30281FCHP [DX3011]
M30290FAHP [DX3016]
M30290FATHP [DX3016]
M30290FAVHP [DX3016]
M30290FCHP [DX3016]
M30290FCTHP [DX3016]
M30290FCVHP [DX3016]
M30291F8HP [DX3011]
M30291F8THP [DX3011]
M30291F8VHP [DX3011]
M30291FAHP [DX3011]
M30291FATHP [DX3011]
M30291FAVHP [DX3011]
M30291FCHP [DX3011]
M30291FCTHP [DX3011]
M30291FCVHP [DX3011]

TEMIC

MICROCONTROLLER

T89C51RD2 [DX0001]
T89C51RD2@PLCC44 [DX2044]
T89C51RD2@PLCC68 [DX2068]
T89C51RD2@TQFP44 [DX3003]
T89F64 [DX0001]
T89F64@PLCC44 [DX2044]
T89F64@TQFP44 [DX3003]
TS87C51RB2 [DX0001]
TS87C51RB2@PLCC44 [DX2044]
TS87C51RB2@TQFP44 [DX3002]
TS87C51RC2 [DX0001]
TS87C51RC2@PLCC44 [DX2044]
TS87C51RC2@TQFP44 [DX3002]
TS87C51RD2 [DX0001]
TS87C51RD2@PLCC44 [DX2044]
TS87C51RD2@TQFP44 [DX3002]
TS87C51U2 [DX0001]
TS87C51U2@PLCC44 [DX2044]
TS87C51U2@TQFP44 [DX3002]
TS87C52X2 [DX0001]
TS87C52X2@PLCC44 [DX2044]
TS87C52X2@TQFP44 [DX3002]
TS87C54X2 [DX0001]
TS87C54X2@PLCC44 [DX2044]
TS87C54X2@TQFP44 [DX3002]
TS87C58X2 [DX0001]
TS87C58X2@PLCC44 [DX2044]
TS87C58X2@TQFP44 [DX3002]
TSC71RBX2 [DX0001]
TSC71RBX2@PLCC44 [DX2044]
TSC71RBX2@TQFP44 [DX3002]
TSC71RCX2 [DX0001]
TSC71RCX2@PLCC44 [DX2044]
TSC71RCX2@TQFP44 [DX3002]
TSC71RDX2 [DX0001]
TSC71RDX2@PLCC44 [DX2044]
TSC71RDX2@PLCC68 [DX2068]
TSC71RDX2@TQFP44 [DX3002]
TSC71RDX2@TQFP64 [DX3012]
TSC87251A1@PLCC44 [DX2044]

TSC87251G1 [DX0001]
TSC87251G1@PLCC44 [DX2004]
TSC87251G1A [DX0001]
TSC87251G1A@PLCC44 [DX2044]
TSC87251G2D [DX0001]
TSC87251G2D@PLCC44 [DX2044]
TSC87251G2D@TQFP44 [DX3003]
TSC87C51 [DX0001]
TSC87C51@PLCC44 [DX2044]
TSC87C51@TQFP44 [DX3002]
TSC87C52 [DX0001]
TSC87C52@PLCC44 [DX2044]
TSC87C52@TQFP44 [DX3002]
TSC87C54 [DX0001]
TSC87C54@PLCC44 [DX2044]
TSC87C54@TQFP44 [DX3002]
TSC87C58 [DX0001]
TSC87C58@PLCC44 [DX2044]
TSC87C58@TQFP44 [DX3002]

TERIDIAN

MICROCONTROLLER

71M6513H-IGT [DX3021-7]
71M6513H-IGTR [DX3021-7]
71M6513-IGT [DX3021-7]
71M6513-IGTR [DX3021-7]
71M6521BE-IGT [DX3011-13]
71M6521BE-IM [DX4026-1]
71M6521DE-IGT [DX3011-13]
71M6521DE-IM [DX4026-1]
71M6521FE-IGT [DX3011-13]
71M6521FE-IM [DX4026-1]

Terra Semiconductor

E(E)PROM/FRAM/NVRAM

TS25L010AP [DX1044#1]
TS25L010AP@SOP8 [DX1044#1]
TS25L020AP [DX1044#1]
TS25L020AP@SOP8 [DX1044#1]
TS25L16AP [DX1044#1]
TS25L16AP@SOP8 [DX1044#1]
TS25L16BP@SOP8 [DX1044#1]
TS25L80AP [DX1044#1]
TS25L80AP@SOP8 [DX1044#1]

TI

E(E)PROM/FRAM/NVRAM

BQ3285 [DX0001]
BQ3287 [DX0001]
BQ3287A [DX0001]
BQ4010 [DX0001]
BQ4010Y [DX0001]
BQ4011 [DX0001]
BQ4011Y [DX0001]
BQ4013 [DX0001]
BQ4013Y [DX0001]
BQ4014 [DX0001]
BQ4014Y [DX0001]
BQ4015 [DX0001]
BQ4015Y [DX0001]
SMJ2516 [DX0001]
SMJ2532 [DX0001]
SMJ2532A [DX0001]
SMJ2716 [DX0001]
SMJ27C256 [DX0001]
SMJ27C256@PLCC32 [DX2032]
SMJ27C512 [DX0001]

SMJ27C512@PLCC32 [DX2032]
TMS2516 [DX0001]
TMS2516JLW [DX0001]
TMS2532 [DX0001]
TMS2532A [DX0001]
TMS25L32 [DX0001]
TMS27128 [DX0001]
TMS27128A [DX0001]
TMS2716 [DX0001]
TMS2732 [DX0001]
TMS2732A [DX0001]
TMS2764 [DX0001]
TMS27C010 [DX0001]
TMS27C010@PLCC32 [DX2032]
TMS27C010@TSOP32 [DX1002]
TMS27C010A [DX0001]
TMS27C010A@PLCC32 [DX2032]
TMS27C010A@TSOP32 [DX1002]
TMS27C020 [DX0001]
TMS27C020@PLCC32 [DX2032]
TMS27C020@TSOP32 [DX1002]
TMS27C040 [DX0001]
TMS27C040@PLCC32 [DX2032]
TMS27C040@TSOP32 [DX1002]
TMS27C128 [DX0001]
TMS27C128@PLCC32
TMS27C2001 [DX0001]
TMS27C2001@PLCC32 [DX2032]
TMS27C2001@TSOP32 [DX1002]
TMS27C210 [DX0001]
TMS27C210@PLCC44 [DX2044]
TMS27C210A [DX0001]
TMS27C210A@PLCC44 [DX2044]
TMS27C240 [DX0001]
TMS27C240@PLCC44 [DX2044]
TMS27C256 [DX0001]
TMS27C256@PLCC32 [DX2032]
TMS27C291 [DX0001]
TMS27C291@PLCC28 [DX2028]
TMS27C292 [DX0001]
TMS27C292@PLCC28 [DX2028]
TMS27C32 [DX0001]
TMS27C512 [DX0001]
TMS27C512@PLCC32 [DX2032]
TMS27C64 [DX0001]
TMS27LV010A [DX0001]
TMS27LV010A@PLCC32 [DX2032]
TMS27LV010A@TSOP32 [DX1002]
TMS27P32A [DX0001]
TMS27P64 [DX0001]
TMS27PC010 [DX0001]
TMS27PC010@PLCC32 [DX2032]
TMS27PC010@TSOP32 [DX1002]
TMS27PC010A [DX0001]
TMS27PC010A@PLCC32 [DX2032]
TMS27PC010A@TSOP32 [DX1002]
TMS27PC020 [DX0001]
TMS27PC020@PLCC32 [DX2032]
TMS27PC020@TSOP32 [DX1002]
TMS27PC040 [DX0001]
TMS27PC040@PLCC32 [DX2032]
TMS27PC040@TSOP32 [DX1002]
TMS27PC128 [DX0001]
TMS27PC128@PLCC32
TMS27PC210 [DX0001]
TMS27PC210@PLCC44 [DX2044]
TMS27PC210A [DX0001]
TMS27PC210A@PLCC44 [DX2044]
TMS27PC240 [DX0001]
TMS27PC240@PLCC44 [DX2044]
TMS27PC256 [DX0001]
TMS27PC256@PLCC32 [DX2032]
TMS27PC291 [DX0001]
TMS27PC291@PLCC28 [DX2028]
TMS27PC32 [DX0001]
TMS27PC32A [DX0001]
TMS27PC512 [DX0001]
TMS27PC512@PLCC32 [DX2032]
TMS27PC64 [DX0001]
TMS28F010 [DX0001]
TMS28F010(REVERSE)@TSOP32 [DX1002]
TMS28F010@PLCC32 [DX2032]
TMS28F010@TSOP32 [DX1002]
TMS28F020 [DX0001]
TMS28F020(REVERSE)@TSOP32 [DX1002]
TMS28F020@PLCC32 [DX2032]
TMS28F020@TSOP32 [DX1002]
TMS28F200AF-B@PSOP44 [DX1014]
TMS28F200AF-B@TSOP48 [DX1004]
TMS28F200AF-T@PSOP44 [DX1014]
TMS28F200AF-T@TSOP48 [DX1004]
TMS28F200BZ-B@PSOP44 [DX1014]
TMS28F200BZ-T@PSOP44 [DX1014]

TMS28F210 [DX0001]
TMS28F210@PLCC44 [DX2044]
TMS28F210@TSOP40 [DX1005]
TMS28F400AE-B@PSOP44 [DX1014]
TMS28F400AE-B@TSOP48 [DX1004]
TMS28F400AE-T@PSOP44 [DX1014]
TMS28F400AE-T@TSOP48 [DX1004]
TMS28F400AF-B@PSOP44 [DX1014]
TMS28F400AF-B@TSOP48 [DX1004]
TMS28F400AF-T@PSOP44 [DX1014]
TMS28F400AF-T@TSOP48 [DX1004]
TMS28F400AM-B@PSOP44 [DX1014]
TMS28F400AM-B@TSOP48 [DX1004]
TMS28F400AM-T@PSOP44 [DX1014]
TMS28F400AM-T@TSOP48 [DX1004]
TMS28F400AS-B@PSOP44 [DX1014]
TMS28F400AS-B@TSOP48 [DX1004]
TMS28F400AS-T@PSOP44 [DX1014]
TMS28F400AS-T@TSOP48 [DX1004]
TMS28F400AZ-B@PSOP44 [DX1014]
TMS28F400AZ-B@TSOP48 [DX1004]
TMS28F400AZ-T@PSOP44 [DX1014]
TMS28F400AZ-T@TSOP48 [DX1004]
TMS28F400BZ-B@PSOP44 [DX1014]
TMS28F400BZ-T@PSOP44 [DX1014]
TMS28F512 [DX0001]
TMS28F512(REVERSE)@TSOP32 [DX1002]
TMS28F512@PLCC32 [DX2032]
TMS28F512@TSOP32 [DX1002]
TMS28F800AE-B@PSOP44 [DX1014]
TMS28F800AE-B@TSOP48 [DX1004]
TMS28F800AE-T@PSOP44 [DX1014]
TMS28F800AE-T@TSOP48 [DX1004]
TMS28F800AL-B@PSOP44 [DX1014]
TMS28F800AL-B@TSOP48 [DX1004]
TMS28F800AL-T@PSOP44 [DX1014]
TMS28F800AL-T@TSOP48 [DX1004]
TMS28F800AS-B@PSOP44 [DX1014]
TMS28F800AS-B@TSOP48 [DX1004]
TMS28F800AS-T@PSOP44 [DX1014]
TMS28F800AS-T@TSOP48 [DX1004]
TMS28F800AV-B@PSOP44 [DX1014]
TMS28F800AV-B@TSOP48 [DX1004]
TMS28F800AV-T@PSOP44 [DX1014]
TMS28F800AV-T@TSOP48 [DX1004]
TMS28F800AZ-B@PSOP44 [DX1014]
TMS28F800AZ-B@TSOP48 [DX1004]
TMS28F800AZ-T@PSOP44 [DX1014]
TMS28F800AZ-T@TSOP48 [DX1004]
TMS28F800SE-B@PSOP44 [DX1014]
TMS28F800SE-B@TSOP48 [DX1004]
TMS28F800SE-T@PSOP44 [DX1014]
TMS28F800SE-T@TSOP48 [DX1004]
TMS28F800SZ-B@PSOP44 [DX1014]
TMS28F800SZ-B@TSOP48 [DX1004]
TMS28F800SZ-T@PSOP44 [DX1014]
TMS28F800SZ-T@TSOP48 [DX1004]
TMS29F040 [DX0001]
TMS29F040@PLCC32 [DX2032]
TMS29F040@TSOP32 [DX1002]
TMS87C257 [DX0001]
TMS87C257@PLCC32 [DX2032]

BPROM

TBP28L42N [DX0001]
TBP28P42 [DX0001]
TBP28S42 [DX0001]
TBP28SA42 [DX0001]

PLD

EP1800@PLCC68 [DX2068]
EP1810@PLCC68 [DX2068]
EP1830@PLCC68 [DX2068]
EP330 [DX0001]
EP330@PLCC20 [DX2020]
EP910 [DX0001]
EP910@PLCC44 [DX2044]
PAL16L8A [DX0001]
PAL16L8A@PLCC20 [DX2020]
PAL16L8A-2 [DX0001]
PAL16L8A-2@PLCC20 [DX2020]
PAL16R4A [DX0001]

PAL16R4A@PLCC20 [DX2020]
PAL16R4A-2@PLCC20 [DX2020]
PAL16R6A@PLCC20 [DX2020]
PAL16R6A-2@PLCC20 [DX2020]
PAL16R8A@PLCC20 [DX2020]
PAL16R8A-2@PLCC20 [DX2020]
TIB82S167A@PLCC28 [DX2028]
TIB82S167B@PLCC28 [DX2028]
TIBPAL16L8-12@PLCC20 [DX2020]
TIBPAL16L8-15@PLCC20 [DX2020]
TIBPAL16L8-25@PLCC20 [DX2020]
TIBPAL16R4-12@PLCC20 [DX2020]
TIBPAL16R4-15@PLCC20 [DX2020]
TIBPAL16R4-25@PLCC20 [DX2020]
TIBPAL16R6-12@PLCC20 [DX2020]
TIBPAL16R6-15@PLCC20 [DX2020]
TIBPAL16R6-25@PLCC20 [DX2020]
TIBPAL16R8-12@PLCC20 [DX2020]
TIBPAL16R8-15@PLCC20 [DX2020]
TIBPAL16R8-25@PLCC20 [DX2020]
TIBPAL20L8-10@PLCC28 [DX2028]
TIBPAL20L8-15@PLCC28 [DX2028]
TIBPAL20L8-25@PLCC28 [DX2028]
TIBPAL20L8-5@PLCC28 [DX2028]
TIBPAL20L8-7@PLCC28 [DX2028]
TIBPAL20R4-10@PLCC28 [DX2028]
TIBPAL20R4-15@PLCC28 [DX2028]
TIBPAL20R4-25@PLCC28 [DX2028]
TIBPAL20R4-5@PLCC28 [DX2028]
TIBPAL20R4-7@PLCC28 [DX2028]
TIBPAL20R6-10@PLCC28 [DX2028]
TIBPAL20R6-15@PLCC28 [DX2028]
TIBPAL20R6-25@PLCC28 [DX2028]
TIBPAL20R6-5@PLCC28 [DX2028]
TIBPAL20R6-7@PLCC28 [DX2028]
TIBPAL20R8-10@PLCC28 [DX2028]
TIBPAL20R8-15@PLCC28 [DX2028]
TIBPAL20R8-25@PLCC28 [DX2028]
TIBPAL20R8-5@PLCC28 [DX2028]
TIBPAL20R8-7@PLCC28 [DX2028]
TIBPAL22V10@PLCC28 [DX2028]
TIBPAL22V10-10@PLCC28 [DX2028]
TIBPAL22V10-15@PLCC28 [DX2028]
TIBPAL22V10-20@PLCC28 [DX2028]
TIBPAL22V10-5@PLCC28 [DX2028]
TIBPAL22V10-7@PLCC28 [DX2028]
TIBPAL22V10A@PLCC28 [DX2028]
TICPAL22V10Z(0 PWR)@PLCC28 [DX2028]
PAL16R4A-2 [DX0001]
PAL16R6A [DX0001]
PAL16R6A-2 [DX0001]
PAL16R8A [DX0001]
PAL16R8A-2 [DX0001]
TIB82S167A [DX0001]
TIB82S167B [DX0001]
TIBPAL16L8-12 [DX0001]
TIBPAL16L8-15 [DX0001]
TIBPAL16L8-25 [DX0001]
TIBPAL16R4-12 [DX0001]
TIBPAL16R4-15 [DX0001]
TIBPAL16R4-25 [DX0001]
TIBPAL16R6-12 [DX0001]
TIBPAL16R6-15 [DX0001]
TIBPAL16R6-25 [DX0001]
TIBPAL16R8-12 [DX0001]
TIBPAL16R8-15 [DX0001]
TIBPAL16R8-25 [DX0001]
TIBPAL20L8-10 [DX0001]
TIBPAL20L8-15 [DX0001]
TIBPAL20L8-25 [DX0001]
TIBPAL20L8-5 [DX0001]
TIBPAL20L8-7 [DX0001]
TIBPAL20R4-10 [DX0001]
TIBPAL20R4-15 [DX0001]
TIBPAL20R4-25 [DX0001]
TIBPAL20R4-5 [DX0001]
TIBPAL20R4-7 [DX0001]
TIBPAL20R6-10 [DX0001]
TIBPAL20R6-15 [DX0001]
TIBPAL20R6-25 [DX0001]
TIBPAL20R6-5 [DX0001]
TIBPAL20R6-7 [DX0001]
TIBPAL20R8-10 [DX0001]
TIBPAL20R8-15 [DX0001]
TIBPAL20R8-25 [DX0001]
TIBPAL20R8-5 [DX0001]
TIBPAL20R8-7 [DX0001]
TIBPAL22V10 [DX0001]
TIBPAL22V10-10 [DX0001]
TIBPAL22V10-15 [DX0001]
TIBPAL22V10-20 [DX0001]
TIBPAL22V10-5 [DX0001]
TIBPAL22V10-7 [DX0001]
TIBPAL22V10A [DX0001]
TICPAL22V10Z(0 PWR) [DX0001]

TICPAL22V10Z(TURBO) [DX0001]
TICPAL22V10Z(TURBO)@PLCC28 [DX2028]

MICROCONTROLLER

BQ2022ADBZR [DX1041]
BQ2022ALPR [DX0001]
BQ2022DBZR [DX1041]
BQ2022LPR [DX0001]
BUF01900@DFN10 [DX4007]
BUF01900@TSSOP8 [DX1001]
BUF01901@DFN10 [DX4007]
BUF01901@TSSOP8 [DX1001]
BUF08630@QFN20 [DX4025]
BUF08821@SSOP20 [DX1001]
BUF08822@SSOP20 [DX1001]
BUF08832@SSOP20 [DX1001]
BUF08832@SSOP20(*) [DX1001]
BUF16820@SSOP32 [DX1027]
BUF16821A@SSOP28 [DX1001]
BUF16821B@SSOP28 [DX1001]
BUF20820@SSOP38 [DX1012]
BUF22821@SSOP38 [DX1012]
CC2530F128@QFN40 [DX4017]
CC2530F256@QFN40 [DX4017]
CC2531F128@QFN40 [DX4017]
CC2531F256@QFN40 [DX4017]
CC2541F128@QFN40 [DX4017]
CC2541F256@QFN40 [DX4017]
CC430F5123IRGZ [DX4021]
CC430F5125IRGZ [DX4021]
CC430F5127IRGZ [DX4021]
CC430F5133IRGZ [DX4021]
CC430F5135IRGZ [DX4021]
CC430F5137IRGZ [DX4021]
CC430F5143IRGZ [DX4021]
CC430F5145IRGZ [DX4021]
CC430F5147IRGZ [DX4021]
CC430F6125IRGC [DX4023]
CC430F6126IRGC [DX4023]
CC430F6127IRGC [DX4023]
CC430F6135IRGC [DX4023]
CC430F6137IRGC [DX4023]
CC430F6143IRGC [DX4023]
CC430F6145IRGC [DX4023]
CC430F6147IRGC [DX4023]
CDCE62005@QFN48 [DX4021]
LM3S1811@BGA108 [DX5107]
LM3S1811@LQFP100 [DX3043]
LM3S1D21@BGA108 [DX5107]
LM3S1D21@LQFP100 [DX3043]
LM3S1R26@LQFP64 [DX3011]
LM3S2793@BGA108 [DX5107]
LM3S2793@LQFP100 [DX3043]
LM3S2D93@BGA108 [DX5107]
LM3S2D93@LQFP100 [DX3043]
LM3S5K31@BGA108 [DX5107]
LM3S5K31@LQFP100 [DX3043]
LM3S5P36@LQFP64 [DX3011]
LM3S5R31@BGA108 [DX5107]
LM3S5R31@LQFP100 [DX3043]
LM3S5R36@LQFP64 [DX3011]
LM3S9B90@BGA108 [DX5107]
LM3S9B90@LQFP100 [DX3043]
LM3S9B92@BGA108 [DX5107]
LM3S9B92@LQFP100 [DX3043]
LM3S9B96@BGA108 [DX5107]
LM3S9B96@LQFP100 [DX3043]
LM3S9D92@BGA108 [DX5107]
LM3S9D92@LQFP100 [DX3043]
LM3S9D96@BGA108 [DX5107]
LM3S9D96@LQFP100 [DX3043]
LM4F110B2QR@LQFP64 [DX3057-9]
LM4F110C4QR@LQFP64 [DX3057-9]
LM4F110E5QR@LQFP64 [DX3057-9]
LM4F110H5QR@LQFP64 [DX3057-9]
LM4F111B2QR@LQFP64 [DX3057-9]
LM4F111C4QR@LQFP64 [DX3057-9]
LM4F111E5QR@LQFP64 [DX3057-9]
LM4F111H5QR@LQFP64 [DX3057-9]
LM4F112C4QC@LQFP100 [DX3043-5]
LM4F112E5QC@LQFP100 [DX3043-5]
LM4F112H5QC@LQFP100 [DX3043-5]
LM4F112H5QD@LQFP144 [DX3051-3]
LM4F120B2QR@LQFP64 [DX3057-9]
LM4F120C4QR@LQFP64 [DX3057-9]
LM4F120E5QR@LQFP64 [DX3057-9]
LM4F120H5QR@LQFP64 [DX3057-9]
LM4F121B2QR@LQFP64 [DX3057-9]

LM4F121C4QR@LQFP64 [DX3057-9]
LM4F121E5QR@LQFP64 [DX3057-9]
LM4F121H5QR@LQFP64 [DX3057-9]
LM4F122C4QC@LQFP100 [DX3043-5]
LM4F122E5QC@LQFP100 [DX3043-5]
LM4F122H5QC@LQFP100 [DX3043-5]
LM4F122H5QD@LQFP144 [DX3051-3]
LM4F130C4QR@LQFP64 [DX3057-9]
LM4F130E5QR@LQFP64 [DX3057-9]
LM4F130H5QR@LQFP64 [DX3057-9]
LM4F131C4QR@LQFP64 [DX3057-9]
LM4F131E5QR@LQFP64 [DX3057-9]
LM4F131H5QR@LQFP64 [DX3057-9]
LM4F132C4QC@LQFP100 [DX3043-5]
LM4F132E5QC@LQFP100 [DX3043-5]
LM4F132H5QC@LQFP100 [DX3043-5]
LM4F132H5QD@LQFP144 [DX3051-3]
LM4F210E5QR@LQFP64 [DX3057-9]
LM4F210H5QR@LQFP64 [DX3057-9]
LM4F211E5QR@LQFP64 [DX3057-9]
LM4F211H5QR@LQFP64 [DX3057-9]
LM4F212E5QC@LQFP100 [DX3043-5]
LM4F212H5QC@LQFP100 [DX3043-5]
LM4F212H5QD@LQFP144 [DX3051-3]
LM4F230E5QR@LQFP64 [DX3057-9]
LM4F230H5QR@LQFP64 [DX3057-9]
LM4F231E5QR@LQFP64 [DX3057-9]
LM4F231H5QR@LQFP64 [DX3057-9]
LM4F232E5QC@LQFP100 [DX3043-5]
LM4F232H5QC@LQFP100 [DX3043-5]
LM4F232H5QD@LQFP144 [DX3051-3]
LSD4FE8231 [DX3011]
LSD4FE8232 [DX3011]
LSD4FE8233 [DX3011]
MSC1210Y2PAGR [DX3057]
MSC1210Y3PAGR [DX3057]
MSC1210Y4PAGR [DX3057]
MSC1210Y5PAGR [DX3057]
MSC1211Y2PAGR [DX3057]
MSC1211Y3PAGR [DX3057]
MSC1211Y4PAGR [DX3057]
MSC1211Y5PAGR [DX3057]
MSC1212Y2PAGR [DX3057]
MSC1212Y3PAGR [DX3057]
MSC1212Y4PAGR [DX3057]
MSC1212Y5PAGR [DX3057]
MSC1213Y2PAGR [DX3057]
MSC1213Y3PAGR [DX3057]
MSC1213Y4PAGR [DX3057]
MSC1213Y5PAGR [DX3057]
MSC1214Y2PAGR [DX3057]
MSC1214Y3PAGR [DX3057]
MSC1214Y4PAGR [DX3057]
MSC1214Y5PAGR [DX3057]
MSP430AFE221AIPW [DX1000]
MSP430AFE221IPW [DX1000]
MSP430AFE222AIPW [DX1000]
MSP430AFE222IPW [DX1000]
MSP430AFE223AIPW [DX1000]
MSP430AFE223IPW [DX1000]
MSP430AFE231AIPW [DX1000]
MSP430AFE231IPW [DX1000]
MSP430AFE232AIPW [DX1000]
MSP430AFE232IPW [DX1000]
MSP430AFE233AIPW [DX1000]
MSP430AFE233IPW [DX1000]
MSP430AFE251AIPW [DX1000]
MSP430AFE251IPW [DX1000]
MSP430AFE252AIPW [DX1000]
MSP430AFE252IPW [DX1000]
MSP430AFE253AIPW [DX1000]
MSP430AFE253IPW [DX1000]
MSP430BT5190IPZ [DX3021]
MSP430BT5190IZQW [DX5150]
MSP430BT6125IRGC [DX4023]
MSP430BT6126IRGC [DX4023]
MSP430BT6127IRGC [DX4023]
MSP430BT6135IRGC [DX4023]
MSP430BT6137IRGC [DX4023]
MSP430BT6143IRGC [DX4023]
MSP430BT6145IRGC [DX4023]
MSP430BT6147IRGC [DX4023]
MSP430F110@SOIC20 [DX1033]
MSP430F110@TSSOP20 [DX1000]
MSP430F1101@SOIC20 [DX1033]
MSP430F1101@TSSOP20 [DX1000]
MSP430F1101A@QFN24 [DX4012]
MSP430F1101A@QFN24(ISP) [DX0001]
MSP430F1101A@SOIC20 [DX1033]
MSP430F1101A@SOIC20(ISP) [DX0001]
MSP430F1101A@TSSOP20 [DX1000]
MSP430F1101A@TSSOP20(ISP) [DX0001]

MSP430F1111A@QFN24 [DX4012]
MSP430F1111A@QFN24(ISP) [DX0001]
MSP430F1111A@SOIC20 [DX1033]
MSP430F1111A@SOIC20(ISP) [DX0001]
MSP430F1111A@TSSOP20 [DX1000]
MSP430F1111A@TSSOP20(ISP) [DX0001]
MSP430F112@SOIC20 [DX1033]
MSP430F112@TSSOP20 [DX1000]
MSP430F1121@SOIC20 [DX1033]
MSP430F1121@TSSOP20 [DX1000]
MSP430F1121A@QFN24 [DX4012]
MSP430F1121A@QFN24(ISP) [DX0001]
MSP430F1121A@SOIC20 [DX1033]
MSP430F1121A@SOIC20(ISP) [DX0001]
MSP430F1121A@TSSOP20 [DX1000]
MSP430F1121A@TSSOP20(ISP) [DX0001]
MSP430F1122@QFN32 [DX4015]
MSP430F1122@SOIC20 [DX1033]
MSP430F1122@TSSOP20 [DX1000]
MSP430F1132@QFN32 [DX4015]
MSP430F1132@SOIC20 [DX1033]
MSP430F1132@TSSOP20 [DX1000]
MSP430F122@QFN32 [DX4015]
MSP430F122@SOIC28 [DX1033]
MSP430F122@TSSOP28 [DX1001]
MSP430F1222@QFN32 [DX4015]
MSP430F1222@SOIC28 [DX1033]
MSP430F1222@TSSOP28 [DX1001]
MSP430F123@QFN32 [DX4015]
MSP430F123@SOIC28 [DX1033]
MSP430F123@TSSOP28 [DX1001]
MSP430F1232@QFN32 [DX4015]
MSP430F1232@SOIC28 [DX1033]
MSP430F1232@TSSOP28 [DX1001]
MSP430F133@QFN64 [DX4023]
MSP430F133@TQFP64 [DX3011]
MSP430F135@QFN64 [DX4023]
MSP430F135@TQFP64 [DX3011]
MSP430F147@QFN64 [DX4023]
MSP430F147@TQFP64 [DX3011]
MSP430F1471@QFN64 [DX4023]
MSP430F1471@TQFP64 [DX3011]
MSP430F148@QFN64 [DX4023]
MSP430F148@TQFP64 [DX3011]
MSP430F1481@QFN64 [DX4023]
MSP430F1481@TQFP64 [DX3011]
MSP430F149@QFN64 [DX4023]
MSP430F149@TQFP64 [DX3011]
MSP430F1491@QFN64 [DX4023]
MSP430F1491@TQFP64 [DX3011]
MSP430F155@QFN64 [DX4023]
MSP430F155@TQFP64 [DX3011]
MSP430F156@QFN64 [DX4023]
MSP430F156@TQFP64 [DX3011]
MSP430F157@QFN64 [DX4023]
MSP430F157@TQFP64 [DX3011]
MSP430F1610@QFN64 [DX4023]
MSP430F1610@TQFP64 [DX3011]
MSP430F1611@QFN64 [DX4023]
MSP430F1611@TQFP64 [DX3011]
MSP430F1612@QFN64 [DX4023]
MSP430F1612@TQFP64 [DX3011]
MSP430F167@QFN64 [DX4023]
MSP430F167@TQFP64 [DX3011]
MSP430F168@QFN64 [DX4023]
MSP430F168@TQFP64 [DX3011]
MSP430F169@QFN64 [DX4023]
MSP430F169@TQFP64 [DX3011]
MSP430F2001IN [DX0001]
MSP430F2001IN(ISP) [DX0001]
MSP430F2001IN(SPW ISP) [DX0001]
MSP430F2001IN(SPW) [DX0001]
MSP430F2001IPW@TSSOP14 [DX1000]
MSP430F2001IPW@TSSOP14(ISP) [DX0001]
MSP430F2001IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2001IPW@TSSOP14(SPW) [DX1000]
MSP430F2001IRSA@QFN16 [DX4010]
MSP430F2001IRSA@QFN16(ISP) [DX0001]
MSP430F2001IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2001IRSA@QFN16(SPW) [DX4010]

MSP430F2001TN [DX0001] MSP430F2001TN(ISP) [DX0001]
MSP430F2001TN(SPW ISP) [DX0001] MSP430F2001TN(SPW) [DX0001]
MSP430F2001TPW@TSSOP14 [DX1000]
MSP430F2001TPW@TSSOP14(ISP) [DX0001]
MSP430F2001TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2001TPW@TSSOP14(SPW) [DX1000]
MSP430F2001TRSA@QFN16 [DX4010]
MSP430F2001TRSA@QFN16(ISP) [DX0001]
MSP430F2001TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2001TRSA@QFN16(SPW) [DX4010]
MSP430F2002IN [DX0001] MSP430F2002IN(ISP) [DX0001]
MSP430F2002IN(SPW ISP) [DX0001] MSP430F2002IN(SPW) [DX0001]
MSP430F2002IPW@TSSOP14 [DX1000]
MSP430F2002IPW@TSSOP14(ISP) [DX0001]
MSP430F2002IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2002IPW@TSSOP14(SPW) [DX1000]
MSP430F2002IRSA@QFN16 [DX4010]
MSP430F2002IRSA@QFN16(ISP) [DX0001]
MSP430F2002IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2002IRSA@QFN16(SPW) [DX4010]
MSP430F2002TN [DX0001] MSP430F2002TN(ISP) [DX0001]
MSP430F2002TN(SPW ISP) [DX0001] MSP430F2002TN(SPW) [DX0001]
MSP430F2002TPW@TSSOP14 [DX1000]
MSP430F2002TPW@TSSOP14(ISP) [DX0001]
MSP430F2002TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2002TPW@TSSOP14(SPW) [DX1000]
MSP430F2002TRSA@QFN16 [DX4010]
MSP430F2002TRSA@QFN16(ISP) [DX0001]
MSP430F2002TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2002TRSA@QFN16(SPW) [DX4010]
MSP430F2003IN [DX0001] MSP430F2003IN(ISP) [DX0001]
MSP430F2003IN(SPW ISP) [DX0001] MSP430F2003IN(SPW) [DX0001]
MSP430F2003IPW@TSSOP14 [DX1000]
MSP430F2003IPW@TSSOP14(ISP) [DX0001]
MSP430F2003IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2003IPW@TSSOP14(SPW) [DX1000]
MSP430F2003IRSA@QFN16 [DX4010]
MSP430F2003IRSA@QFN16(ISP) [DX0001]
MSP430F2003IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2003IRSA@QFN16(SPW) [DX4010]
MSP430F2003TN [DX0001] MSP430F2003TN(ISP) [DX0001]
MSP430F2003TN(SPW ISP) [DX0001] MSP430F2003TN(SPW) [DX0001]
MSP430F2003TPW@TSSOP14 [DX1000]
MSP430F2003TPW@TSSOP14(ISP) [DX0001]
MSP430F2003TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2003TPW@TSSOP14(SPW) [DX1000]
MSP430F2003TRSA@QFN16 [DX4010]
MSP430F2003TRSA@QFN16(ISP) [DX0001]

MSP430F2003TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2003TRSA@QFN16(SPW) [DX4010]
MSP430F2011IN [DX0001]
MSP430F2011IN(ISP) [DX0001]
MSP430F2011IN(SPW ISP) [DX0001]
MSP430F2011IN(SPW) [DX0001]
MSP430F2011IPW@TSSOP14 [DX1000]
MSP430F2011IPW@TSSOP14(ISP) [DX0001]
MSP430F2011IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2011IPW@TSSOP14(SPW) [DX1000]
MSP430F2011IRSA@QFN16 [DX4010]
MSP430F2011IRSA@QFN16(ISP) [DX0001]
MSP430F2011IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2011IRSA@QFN16(SPW) [DX4010]
MSP430F2011TN [DX0001]
MSP430F2011TN(ISP) [DX0001]
MSP430F2011TN(SPW ISP) [DX0001]
MSP430F2011TN(SPW) [DX0001]
MSP430F2011TPW@TSSOP14 [DX1000]
MSP430F2011TPW@TSSOP14(ISP) [DX0001]
MSP430F2011TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2011TPW@TSSOP14(SPW) [DX1000]
MSP430F2011TRSA@QFN16 [DX4010]
MSP430F2011TRSA@QFN16(ISP) [DX0001]
MSP430F2011TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2011TRSA@QFN16(SPW) [DX4010]
MSP430F2012IN [DX0001]
MSP430F2012IN(ISP) [DX0001]
MSP430F2012IN(SPW ISP) [DX0001]
MSP430F2012IN(SPW) [DX0001]
MSP430F2012IPW@TSSOP14 [DX1000]
MSP430F2012IPW@TSSOP14(ISP) [DX0001]
MSP430F2012IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2012IPW@TSSOP14(SPW) [DX1000]
MSP430F2012IRSA@QFN16 [DX4010]
MSP430F2012IRSA@QFN16(ISP) [DX0001]
MSP430F2012IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2012IRSA@QFN16(SPW) [DX4010]
MSP430F2012TN [DX0001]
MSP430F2012TN(ISP) [DX0001]
MSP430F2012TN(SPW ISP) [DX0001]
MSP430F2012TN(SPW) [DX0001]
MSP430F2012TPW@TSSOP14 [DX1000]
MSP430F2012TPW@TSSOP14(ISP) [DX0001]
MSP430F2012TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2012TPW@TSSOP14(SPW) [DX1000]
MSP430F2012TRSA@QFN16 [DX4010]
MSP430F2012TRSA@QFN16(ISP) [DX0001]
MSP430F2012TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2012TRSA@QFN16(SPW) [DX4010]
MSP430F2013IN [DX0001]
MSP430F2013IN(ISP) [DX0001]
MSP430F2013IN(SPW ISP) [DX0001]
MSP430F2013IN(SPW) [DX0001]
MSP430F2013IPW@TSSOP14 [DX1000]
MSP430F2013IPW@TSSOP14(ISP) [DX0001]
MSP430F2013IPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2013IPW@TSSOP14(SPW) [DX1000]

MSP430F2013IRSA@QFN16 [DX4010]
MSP430F2013IRSA@QFN16(ISP) [DX0001]
MSP430F2013IRSA@QFN16(SPW ISP) [DX0001]
MSP430F2013IRSA@QFN16(SPW) [DX4010]
MSP430F2013TN [DX0001]
MSP430F2013TN(ISP) [DX0001]
MSP430F2013TN(SPW ISP) [DX0001]
MSP430F2013TN(SPW) [DX0001]
MSP430F2013TPW@TSSOP14 [DX1000]
MSP430F2013TPW@TSSOP14(ISP) [DX0001]
MSP430F2013TPW@TSSOP14(SPW ISP) [DX0001]
MSP430F2013TPW@TSSOP14(SPW) [DX1000]
MSP430F2013TRSA@QFN16 [DX4010]
MSP430F2013TRSA@QFN16(ISP) [DX0001]
MSP430F2013TRSA@QFN16(SPW ISP) [DX0001]
MSP430F2013TRSA@QFN16(SPW) [DX4010]
MSP430F2101@QFN24 [DX4012]
MSP430F2101@QFN24(ISP) [DX0001]
MSP430F2101@SOIC20 [DX1033]
MSP430F2101@SOIC20(ISP) [DX0001]
MSP430F2101@TSSOP20 [DX1001]
MSP430F2101@TSSOP20(ISP) [DX0001]
MSP430F2101@TVSOP20 [DX1023]
MSP430F2101@TVSOP20(ISP) [DX0001]
MSP430F2111@QFN24 [DX4012]
MSP430F2111@QFN24(ISP) [DX0001]
MSP430F2111@SOIC20 [DX1033]
MSP430F2111@SOIC20(ISP) [DX0001]
MSP430F2111@TSSOP20 [DX1001]
MSP430F2111@TSSOP20(ISP) [DX0001]
MSP430F2111@TVSOP20 [DX1023]
MSP430F2111@TVSOP20(ISP) [DX0001]
MSP430F2112AIPW@TSSOP28 [DX1001]
MSP430F2112AIRHB@QFN32 [DX4015]
MSP430F2112ATPW@TSSOP28 [DX1001]
MSP430F2112ATRHB@QFN32 [DX4015]
MSP430F2112IPW@TSSOP28 [DX1001]
MSP430F2112IRHB@QFN32 [DX4015]
MSP430F2112TPW@TSSOP28 [DX1001]
MSP430F2112TRHB@QFN32 [DX4015]
MSP430F2121@QFN24 [DX4012]
MSP430F2121@QFN24(ISP) [DX0001]
MSP430F2121@SOIC20 [DX1033]
MSP430F2121@SOIC20(ISP) [DX0001]
MSP430F2121@TSSOP20 [DX1001]
MSP430F2121@TSSOP20(ISP) [DX0001]
MSP430F2121@TVSOP20 [DX1023]
MSP430F2121@TVSOP20(ISP) [DX0001]
MSP430F2122AIPW@TSSOP28 [DX1001]
MSP430F2122AIRHB@QFN32 [DX4015]
MSP430F2122ATPW@TSSOP28 [DX1001]
MSP430F2122ATRHB@QFN32 [DX4015]
MSP430F2122IPW@TSSOP28 [DX1001]
MSP430F2122IRHB@QFN32 [DX4015]
MSP430F2122TPW@TSSOP28 [DX1001]
MSP430F2122TRHB@QFN32 [DX4015]
MSP430F2131@QFN24 [DX4012]
MSP430F2131@QFN24(ISP) [DX0001]
MSP430F2131@SOIC20 [DX1033]
MSP430F2131@SOIC20(ISP) [DX0001]
MSP430F2131@TSSOP20 [DX1001]
MSP430F2131@TSSOP20(ISP) [DX0001]
MSP430F2131@TVSOP20 [DX1023]
MSP430F2131@TVSOP20(ISP) [DX0001]
MSP430F2132AIPW@TSSOP28 [DX1001]
MSP430F2132AIRHB@QFN32 [DX4015]
MSP430F2132ATPW@TSSOP28 [DX1001]
MSP430F2132ATRHB@QFN32 [DX4015]

MSP430F2132IPW@TSSOP28 [DX1001]
MSP430F2132IRHB@QFN32 [DX4015]
MSP430F2132TPW@TSSOP28 [DX1001]
MSP430F2132TRHB@QFN32 [DX4015]
MSP430F2232IDA@SSOP38 [DX1027]
MSP430F2232IDA@SSOP38(ISP) [DX0001]
MSP430F2232IRHA@QFN40 [DX4017]
MSP430F2232IRHA@QFN40(ISP) [DX0001]
MSP430F2232IYFF [BBBB]
MSP430F2232IYFF(ISP) [BBBB]
MSP430F2232TDA@SSOP38 [DX1027]
MSP430F2232TDA@SSOP38(ISP) [DX0001]
MSP430F2232TRHA@QFN40 [DX4017]
MSP430F2232TRHA@QFN40(ISP) [DX0001]
MSP430F2232TYFF [BBBB]
MSP430F2232TYFF(ISP) [DX0001]
MSP430F2234IDA@SSOP38 [DX1027]
MSP430F2234IDA@SSOP38(ISP) [DX0001]
MSP430F2234IRHA@QFN40 [DX4017]
MSP430F2234IRHA@QFN40(ISP) [DX0001]
MSP430F2234IYFF [BBBB]
MSP430F2234IYFF(ISP) [DX0001]
MSP430F2234TDA@SSOP38 [DX1027]
MSP430F2234TDA@SSOP38(ISP) [DX0001]
MSP430F2234TRHA@QFN40 [DX4017]
MSP430F2234TRHA@QFN40(ISP) [DX0001]
MSP430F2234TYFF [BBBB]
MSP430F2234TYFF(ISP) [DX0001]
MSP430F2252IDA@SSOP38 [DX1027]
MSP430F2252IDA@SSOP38(ISP) [DX0001]
MSP430F2252IRHA@QFN40 [DX4017]
MSP430F2252IRHA@QFN40(ISP) [DX0001]
MSP430F2252IYFF [BBBB]
MSP430F2252IYFF(ISP) [DX0001]
MSP430F2252TDA@SSOP38 [DX1027]
MSP430F2252TDA@SSOP38(ISP) [DX0001]
MSP430F2252TRHA@QFN40 [DX4017]
MSP430F2252TRHA@QFN40(ISP) [DX0001]
MSP430F2252TYFF [BBBB]
MSP430F2252TYFF(ISP) [DX0001]
MSP430F2254IDA@SSOP38 [DX1027]
MSP430F2254IDA@SSOP38(ISP) [DX0001]
MSP430F2254IRHA@QFN40 [DX4017]
MSP430F2254IRHA@QFN40(ISP) [DX0001]
MSP430F2254IYFF [BBBB]
MSP430F2254IYFF(ISP) [DX0001]
MSP430F2254TDA@SSOP38 [DX1027]
MSP430F2254TDA@SSOP38(ISP) [DX0001]
MSP430F2254TRHA@QFN40 [DX4017]
MSP430F2254TRHA@QFN40(ISP) [DX0001]
MSP430F2254TYFF [BBBB]
MSP430F2254TYFF(ISP) [DX0001]
MSP430F2272IDA@SSOP38 [DX1027]
MSP430F2272IDA@SSOP38(ISP) [DX0001]
MSP430F2272IRHA@QFN40 [DX4017]
MSP430F2272IRHA@QFN40(ISP) [DX0001]
MSP430F2272IYFF [BBBB]
MSP430F2272IYFF(ISP) [DX0001]
MSP430F2272TDA@SSOP38 [DX1027]

MSP430F2272TDA@SSOP38(ISP) [DX0001]
MSP430F2272TRHA@QFN40 [DX4017]
MSP430F2272TRHA@QFN40(ISP) [DX0001]
MSP430F2272TYFF [BBBB]
MSP430F2272TYFF(ISP) [DX0001]
MSP430F2274IDA@SSOP38 [DX1027]
MSP430F2274IDA@SSOP38(ISP) [DX0001]
MSP430F2274IRHA@QFN40 [DX4017]
MSP430F2274IRHA@QFN40(ISP) [DX0001]
MSP430F2274IYFF [BBBB]
MSP430F2274IYFF(ISP) [DX0001]
MSP430F2274TDA@SSOP38 [DX1027]
MSP430F2274TDA@SSOP38(ISP) [DX0001]
MSP430F2274TRHA@QFN40 [DX4017]
MSP430F2274TRHA@QFN40(ISP) [DX0001]
MSP430F2274TYFF [BBBB]
MSP430F2274TYFF(ISP) [DX0001]
MSP430F233@LQFP64 [DX3011]
MSP430F233@QFN64 [DX4023]
MSP430F2330IRHA@QFN40 [DX4017]
MSP430F2330IRHA@QFN40(ISP) [DX0001]
MSP430F2330TRHA@QFN40 [DX4017]
MSP430F2330TRHA@QFN40(ISP) [DX0001]
MSP430F235@LQFP64 [DX3011]
MSP430F235@QFN64 [DX4023]
MSP430F2350IRHA@QFN40 [DX4017]
MSP430F2350IRHA@QFN40(ISP) [DX0001]
MSP430F2350TRHA@QFN40 [DX4017]
MSP430F2350TRHA@QFN40(ISP) [DX0001]
MSP430F2370IRHA@QFN40 [DX4017]
MSP430F2370IRHA@QFN40(ISP) [DX0001]
MSP430F2370TRHA@QFN40 [DX4017]
MSP430F2370TRHA@QFN40(ISP) [DX0001]
MSP430F2410@QFN64 [DX4023]
MSP430F2410@TQFP64 [DX3011]
MSP430F2410TZQW [DX5150]
MSP430F2416@TQFP64 [DX3011]
MSP430F2416@TQFP80 [DX3016]
MSP430F2416TZQW [DX5150]
MSP430F2417@TQFP64 [DX3011]
MSP430F2417@TQFP80 [DX3016]
MSP430F2417TZQW [DX5150]
MSP430F2418@TQFP64 [DX3011]
MSP430F2418@TQFP80 [DX3016]
MSP430F2418TZQW [DX5150]
MSP430F2419@TQFP64 [DX3011]
MSP430F2419@TQFP80 [DX3016]
MSP430F2419TZQW [DX5150]
MSP430F247@QFN64 [DX4023]
MSP430F247@TQFP64 [DX3011]
MSP430F2471@QFN64 [DX4023]
MSP430F2471@TQFP64 [DX3011]
MSP430F248@QFN64 [DX4023]
MSP430F248@TQFP64 [DX3011]
MSP430F2481@QFN64 [DX4023]
MSP430F2481@TQFP64 [DX3011]
MSP430F249@QFN64 [DX4023]
MSP430F249@TQFP64 [DX3011]
MSP430F2491@QFN64 [DX4023]
MSP430F2491@TQFP64 [DX3011]
MSP430F2491A@QFN64 [DX4023]
MSP430F2491A@TQFP64 [DX3011]
MSP430F249A@QFN64 [DX4023]
MSP430F249A@TQFP64 [DX3011]
MSP430F2616@TQFP64 [DX3011]
MSP430F2616@TQFP80 [DX3016]
MSP430F2616TZQW [DX5150]
MSP430F2617@TQFP64 [DX3011]
MSP430F2617@TQFP80 [DX3016]
MSP430F2617TZQW [DX5150]
MSP430F2618@TQFP64 [DX3011]
MSP430F2618@TQFP80 [DX3016]
MSP430F2618TZQW [DX5150]

MSP430F2619@TQFP64 [DX3011]
MSP430F2619@TQFP80 [DX3016]
MSP430F2619TZQW [DX5150]
MSP430F412@QFN64 [DX4023]
MSP430F412@TQFP64 [DX3011]
MSP430F413@QFN64 [DX4023]
MSP430F413@TQFP64 [DX3011]
MSP430F4132@QFN48 [DX4021]
MSP430F4132@QFP64 [DX3011]
MSP430F415@QFN64 [DX4023]
MSP430F415@TQFP64 [DX3011]
MSP430F4152@QFN48 [DX4021]
MSP430F4152@QFP64 [DX3011]
MSP430F417@QFN64 [DX4023]
MSP430F417@TQFP64 [DX3011]
MSP430F423@TQFP64 [DX3011]
MSP430F425@TQFP64 [DX3011]
MSP430F4250@QFN48 [DX4021]
MSP430F4250@SSOP48 [DX1028]
MSP430F4260@QFN48 [DX4021]
MSP430F4260@SSOP48 [DX1028]
MSP430F427@TQFP64 [DX3011]
MSP430F4270@QFN48 [DX4021]
MSP430F4270@SSOP48 [DX1028]
MSP430F428@TQFP64 [DX3011]
MSP430F429@TQFP64 [DX3011]
MSP430F435@TQFP100 [DX3021]
MSP430F435@TQFP80 [DX3016]
MSP430F4351@TQFP100 [DX3021]
MSP430F4351@TQFP80 [DX3016]
MSP430F436@TQFP100 [DX3021]
MSP430F436@TQFP80 [DX3016]
MSP430F4361@TQFP100 [DX3021]
MSP430F4361@TQFP80 [DX3016]
MSP430F437@TQFP100 [DX3021]
MSP430F437@TQFP80 [DX3016]
MSP430F4371@TQFP100 [DX3021]
MSP430F4371@TQFP80 [DX3016]
MSP430F438@TQFP100 [DX3021]
MSP430F438@TQFP80 [DX3016]
MSP430F4381@TQFP100 [DX3021]
MSP430F4381@TQFP80 [DX3016]
MSP430F439@TQFP100 [DX3021]
MSP430F439@TQFP80 [DX3016]
MSP430F4391@TQFP100 [DX3021]
MSP430F4391@TQFP80 [DX3016]
MSP430F447@TQFP100 [DX3021]
MSP430F4471@TQFP100 [DX3021]
MSP430F448@TQFP100 [DX3021]
MSP430F4481@TQFP100 [DX3021]
MSP430F449@TQFP100 [DX3021]
MSP430F4491@TQFP100 [DX3021]
MSP430F46161IPZ@TQFP100 [DX3021]
MSP430F46161IPZR@TQFP100 [DX3021]
MSP430F4616IPZ@TQFP100 [DX3021]
MSP430F4616IPZR@TQFP100 [DX3021]
MSP430F46171IPZ@TQFP100 [DX3021]
MSP430F46171IPZR@TQFP100 [DX3021]
MSP430F4617IPZ@TQFP100 [DX3021]
MSP430F4617IPZR@TQFP100 [DX3021]
MSP430F46181IPZ@TQFP100 [DX3021]
MSP430F46181IPZR@TQFP100 [DX3021]
MSP430F4618IPZ@TQFP100 [DX3021]
MSP430F4618IPZR@TQFP100 [DX3021]
MSP430F46191IPZ@TQFP100 [DX3021]
MSP430F46191IPZR@TQFP100 [DX3021]
MSP430F4619IPZ@TQFP100 [DX3021]
MSP430F4619IPZR@TQFP100 [DX3021]
MSP430F4683IPZ [DX3021]
MSP430F4684IPZ [DX3021]
MSP430F4693IPZ [DX3021]
MSP430F4694IPZ [DX3021]
MSP430F47126@LQFP100 [DX3021]
MSP430F47127@LQFP100 [DX3021]
MSP430F47163@LQFP100 [DX3021]
MSP430F47166@LQFP100 [DX3021]
MSP430F47167@LQFP100 [DX3021]
MSP430F47173@LQFP100 [DX3021]
MSP430F47176@LQFP100 [DX3021]
MSP430F47177@LQFP100 [DX3043]
MSP430F47183@LQFP100 [DX3021]
MSP430F47186@LQFP100 [DX3021]
MSP430F47187@LQFP100 [DX3021]
MSP430F47187@LQFP100(BOT) [DX3110]
MSP430F47193@LQFP100 [DX3021]
MSP430F47196@LQFP100 [DX3021]

MSP430F47197@LQFP100 [DX3021]
MSP430F477@LQFP80 [DX3016]
MSP430F478@LQFP80 [DX3016]
MSP430F4783IPZ@QFP100 [DX3021]
MSP430F4784IPZ@QFP100 [DX3021]
MSP430F479@LQFP80 [DX3016]
MSP430F4793IPZ@QFP100 [DX3021]
MSP430F4794IPZ@QFP100 [DX3021]
MSP430F5131IDA [DX1027]
MSP430F5131IRSB [DX4039]
MSP430F5132IDA [DX1027]
MSP430F5132IRSB [DX4039]
MSP430F5151IDA [DX1027]
MSP430F5151IRSB [DX4039]
MSP430F5152IDA [DX1027]
MSP430F5152IRSB [DX4039]
MSP430F5171IDA [DX1027]
MSP430F5171IRSB [DX4039]
MSP430F5172IDA [DX1027]
MSP430F5172IRSB [DX4039]
MSP430F5232IRGZR [DX4021]
MSP430F5232IRGZT [DX4021]
MSP430F5234IRGZR [DX4021]
MSP430F5234IRGZT [DX4021]
MSP430F5237IRGCR [DX4023]
MSP430F5237IRGCT [DX4023]
MSP430F5237IZQER [DX5191]
MSP430F5237IZQET [DX5191]
MSP430F5239IRGCR [DX4023]
MSP430F5239IRGCT [DX4023]
MSP430F5239IZQER [DX5191]
MSP430F5239IZQET [DX5191]
MSP430F5242IRGZR [DX4021]
MSP430F5242IRGZT [DX4021]
MSP430F5244IRGZR [DX4021]
MSP430F5244IRGZT [DX4021]
MSP430F5247IRGCR [DX4023]
MSP430F5247IRGCT [DX4023]
MSP430F5247IZQER [DX5191]
MSP430F5247IZQET [DX5191]
MSP430F5249IRGCR [DX4023]
MSP430F5249IRGCT [DX4023]
MSP430F5249IZQER [DX5191]
MSP430F5249IZQET [DX5191]
MSP430F5252IRGCR [DX4023]
MSP430F5252IRGCT [DX4023]
MSP430F5252IZQER [DX5191]
MSP430F5252IZQET [DX5191]
MSP430F5253IRGCR [DX4023]
MSP430F5253IRGCT [DX4023]
MSP430F5253IZQER [DX5191]
MSP430F5253IZQET [DX5191]
MSP430F5254IRGCR [DX4023]
MSP430F5254IRGCT [DX4023]
MSP430F5254IZQER [DX5191]
MSP430F5254IZQET [DX5191]
MSP430F5255IRGCR [DX4023]
MSP430F5255IRGCT [DX4023]
MSP430F5255IZQER [DX5191]
MSP430F5255IZQET [DX5191]
MSP430F5256IRGCR [DX4023]
MSP430F5256IRGCT [DX4023]
MSP430F5256IZQER [DX5191]
MSP430F5256IZQET [DX5191]
MSP430F5257IRGCR [DX4023]
MSP430F5257IRGCT [DX4023]
MSP430F5257IZQER [DX5191]
MSP430F5257IZQET [DX5191]
MSP430F5258IRGCR [DX4023]
MSP430F5258IRGCT [DX4023]
MSP430F5258IZQER [DX5191]
MSP430F5258IZQET [DX5191]
MSP430F5259IRGCR [DX4023]
MSP430F5259IRGCT [DX4023]
MSP430F5259IZQER [DX5191]
MSP430F5259IZQET [DX5191]
MSP430F5304IPT [DX3007]
MSP430F5304IRGC [DX4023]
MSP430F5304IRGZ [DX4021]
MSP430F5304IZQE [DX0001]
MSP430F5308IPT [DX3007]
MSP430F5308IRGC [DX4023]
MSP430F5308IRGZ [DX4021]
MSP430F5308IZQE [DX0001]
MSP430F5309IPT [DX3007]
MSP430F5309IRGC [DX4023]
MSP430F5309IRGZ [DX4021]
MSP430F5309IZQE [DX0001]
MSP430F5310IPT [DX3007]
MSP430F5310IRGC [DX4023]
MSP430F5310IRGZ [DX4021]
MSP430F5310IZQE [DX0001]
MSP430F5324IRGC [DX4023]
MSP430F5325IPN [DX3016]
MSP430F5325IZQE [DX0001]
MSP430F5326IRGC [DX4023]

MSP430F5327IPN [DX3016]
MSP430F5327IZQE [DX0001]
MSP430F5328IRGC [DX4023]
MSP430F5329IPN [DX3016]
MSP430F5329IZQE [DX0001]
MSP430F5333AIPZ [DX3021]
MSP430F5333AIZQW [DX5150]
MSP430F5333IPZ [DX3021]
MSP430F5333IZQW [DX5150]
MSP430F5334AIPZ [DX3021]
MSP430F5334AIZQW [DX5150]
MSP430F5334IPZ [DX3021]
MSP430F5334IZQW [DX5150]
MSP430F5335AIPZ [DX3021]
MSP430F5335AIZQW [DX5150]
MSP430F5335IPZ [DX3021]
MSP430F5335IZQW [DX5150]
MSP430F5336AIPZ [DX3021]
MSP430F5336AIZQW [DX5150]
MSP430F5336IPZ [DX3021]
MSP430F5336IZQW [DX5150]
MSP430F5338AIPZ [DX3021]
MSP430F5338AIZQW [DX5150]
MSP430F5338IPZ [DX3021]
MSP430F5338IZQW [DX5150]
MSP430F5340IRGZ [DX4021]
MSP430F5341IRGZ [DX4021]
MSP430F5342IRGZ [DX4021]
MSP430F5358AIPZ [DX3021]
MSP430F5358AIZWQ [DX5150]
MSP430F5359AIPZ [DX3021]
MSP430F5359AIZWQ [DX5150]
MSP430F5418@QFP80 [DX3016]
MSP430F5418A@QFP80 [DX3016]
MSP430F5419@QFP100 [DX3021]
MSP430F5419A@BGA113 [DX5150]
MSP430F5419A@QFP100 [DX3021]
MSP430F5435@QFP80 [DX3016]
MSP430F5435A@QFP80 [DX3016]
MSP430F5436@QFP100 [DX3021]
MSP430F5436A@BGA113 [DX5150]
MSP430F5436A@QFP100 [DX3021]
MSP430F5437@QFP80 [DX3016]
MSP430F5437A@QFP80 [DX3016]
MSP430F5438@QFP100 [DX3021]
MSP430F5438A@BGA113 [DX5150]
MSP430F5438A@QFP100 [DX3021]
MSP430F5500@BGA80 [DX0001]
MSP430F5500@QFN48 [DX4021]
MSP430F5500@QFN64 [DX4023]
MSP430F5500@QFP48 [DX3007]
MSP430F5500IPT [DX3007]
MSP430F5500IRGC [DX4023]
MSP430F5500IRGZ [DX4021]
MSP430F5500IZQE [DX0001]
MSP430F5501@BGA80 [DX0001]
MSP430F5501@QFN48 [DX4021]
MSP430F5501@QFN64 [DX4023]
MSP430F5501@QFP48 [DX3007]
MSP430F5501IPT [DX3007]
MSP430F5501IRGC [DX4023]
MSP430F5501IRGZ [DX4021]
MSP430F5501IZQE [DX0001]
MSP430F5502@BGA80 [DX0001]
MSP430F5502@QFN48 [DX4021]
MSP430F5502@QFN64 [DX4023]
MSP430F5502@QFP48 [DX3007]
MSP430F5502IPT [DX3007]
MSP430F5502IRGC [DX4023]
MSP430F5502IRGZ [DX4021]
MSP430F5502IZQE [DX0001]
MSP430F5503@BGA80 [DX0001]
MSP430F5503@QFN48 [DX4021]
MSP430F5503@QFN64 [DX4023]
MSP430F5503@QFP48 [DX3007]
MSP430F5503IPT [DX3007]
MSP430F5503IRGC [DX4023]
MSP430F5503IRGZ [DX4021]
MSP430F5503IZQE [DX0001]
MSP430F5504@BGA80 [DX0001]
MSP430F5504@QFN48 [DX4021]
MSP430F5504@QFN64 [DX4023]
MSP430F5504@QFP48 [DX3007]
MSP430F5504IPT [DX3007]
MSP430F5504IRGC [DX4023]
MSP430F5504IRGZ [DX4021]
MSP430F5504IZQE [DX0001]
MSP430F5505@BGA80 [DX0001]
MSP430F5505@QFN48 [DX4021]
MSP430F5505@QFN64 [DX4023]
MSP430F5505@QFP48 [DX3007]
MSP430F5505IPT [DX3007]
MSP430F5505IRGC [DX4023]
MSP430F5505IRGZ [DX4021]
MSP430F5505IZQE [DX0001]
MSP430F5506@BGA80 [DX0001]

MSP430F5506@QFN48 [DX4021]
MSP430F5506@QFN64 [DX4023]
MSP430F5506@QFP48 [DX3007]
MSP430F5506IPT [DX3007]
MSP430F5506IRGC [DX4023]
MSP430F5506IRGZ [DX4021]
MSP430F5506IZQE [DX0001]
MSP430F5507@BGA80 [DX0001]
MSP430F5507@QFN48 [DX4021]
MSP430F5507@QFN64 [DX4023]
MSP430F5507@QFP48 [DX3007]
MSP430F5507IPT [DX3007]
MSP430F5507IRGC [DX4023]
MSP430F5507IRGZ [DX4021]
MSP430F5507IZQE [DX0001]
MSP430F5508@BGA80 [DX0001]
MSP430F5508@QFN48 [DX4021]
MSP430F5508@QFN64 [DX4023]
MSP430F5508@QFP48 [DX3007]
MSP430F5508IPT [DX3007]
MSP430F5508IRGC [DX4023]
MSP430F5508IRGZ [DX4021]
MSP430F5508IZQE [DX0001]
MSP430F5509@BGA80 [DX0001]
MSP430F5509@QFN48 [DX4021]
MSP430F5509@QFN64 [DX4023]
MSP430F5509@QFP48 [DX3007]
MSP430F5509IPT [DX3007]
MSP430F5509IRGC [DX4023]
MSP430F5509IRGZ [DX4021]
MSP430F5509IZQE [DX0001]
MSP430F5510@BGA80 [DX0001]
MSP430F5510@QFN48 [DX4021]
MSP430F5510@QFN64 [DX4023]
MSP430F5510@QFP48 [DX3007]
MSP430F5510IPT [DX3007]
MSP430F5510IRGC [DX4023]
MSP430F5510IRGZ [DX4021]
MSP430F5510IZQE [DX0001]
MSP430F5511@QFP80 [DX3016]
MSP430F5513@QFN64 [DX4023]
MSP430F5513IZQE [DX5191]
MSP430F5514@QFN64 [DX4023]
MSP430F5514IZQE [DX5191]
MSP430F5515@QFP80 [DX3016]
MSP430F5517@QFP80 [DX3016]
MSP430F5519@QFP80 [DX3016]
MSP430F5521@QFP80 [DX3016]
MSP430F5522@QFN64 [DX4023]
MSP430F5522IZQE [DX5191]
MSP430F5524@QFN64 [DX4023]
MSP430F5524IZQE [DX5191]
MSP430F5525@QFP80 [DX3016]
MSP430F5526@QFN64 [DX4023]
MSP430F5526IZQE [DX5191]
MSP430F5527@QFP80 [DX3016]
MSP430F5528@QFN64 [DX4023]
MSP430F5528IZQE [DX5191]
MSP430F5529@QFP80 [DX3016]
MSP430F5630AIPZ [DX3021]
MSP430F5630AIZWQ [DX5150]
MSP430F5630IPZ [DX3021]
MSP430F5630IZWQ [DX5150]
MSP430F5631AIPZ [DX3021]
MSP430F5631AIZWQ [DX5150]
MSP430F5631IPZ [DX3021]
MSP430F5631IZWQ [DX5150]
MSP430F5632AIPZ [DX3021]
MSP430F5632AIZWQ [DX5150]
MSP430F5632IPZ [DX3021]
MSP430F5632IZWQ [DX5150]
MSP430F5633AIPZ [DX3021]
MSP430F5633AIZWQ [DX5150]
MSP430F5633IPZ [DX3021]
MSP430F5633IZWQ [DX5150]
MSP430F5634AIPZ [DX3021]
MSP430F5634AIZWQ [DX5150]
MSP430F5634IPZ [DX3021]
MSP430F5634IZWQ [DX5150]
MSP430F5635AIPZ [DX3021]
MSP430F5635AIZWQ [DX5150]
MSP430F5635IPZ [DX3021]
MSP430F5635IZWQ [DX5150]
MSP430F5636AIPZ [DX3021]
MSP430F5636AIZWQ [DX5150]
MSP430F5636IPZ [DX3021]
MSP430F5636IZWQ [DX5150]
MSP430F5637AIPZ [DX3021]
MSP430F5637AIZWQ [DX5150]
MSP430F5637IPZ [DX3021]
MSP430F5637IZWQ [DX5150]
MSP430F5638AIPZ [DX3021]
MSP430F5638AIZWQ [DX5150]
MSP430F5638IPZ [DX3021]
MSP430F5638IZWQ [DX5150]
MSP430F5658AIPZ [DX3021]

MSP430F5658AIZWQ [DX5150]
MSP430F5659AIZWQ [DX5150]
MSP430F6433AIZQW [DX5150]
MSP430F6433IZQW [DX5150]
MSP430F6434AIZQW [DX5150]
MSP430F6434IZQW [DX5150]
MSP430F6435AIZQW [DX5150]
MSP430F6435IZQW [DX5150]
MSP430F6436AIZQW [DX5150]
MSP430F6436IZQW [DX5150]
MSP430F6438AIZQW [DX5150]
MSP430F6438IZQW [DX5150]
MSP430F6458AIZWQ [DX5150]
MSP430F6459AIZWQ [DX5150]
MSP430F6630AIZWQ [DX5150]
MSP430F6630IZWQ [DX5150]
MSP430F6631AIZWQ [DX5150]
MSP430F6631IZWQ [DX5150]
MSP430F6632AIZWQ [DX5150]
MSP430F6632IZWQ [DX5150]
MSP430F6633AIZWQ [DX5150]
MSP430F6633IZWQ [DX5150]
MSP430F6634AIZWQ [DX5150]
MSP430F6634IZWQ [DX5150]
MSP430F6635AIZWQ [DX5150]
MSP430F6635IZWQ [DX5150]
MSP430F6636AIZWQ [DX5150]
MSP430F6636IZWQ [DX5150]
MSP430F6637AIZWQ [DX5150]
MSP430F6637IZWQ [DX5150]
MSP430F6638AIZWQ [DX5150]
MSP430F6638IZWQ [DX5150]
MSP430F6658AIZWQ [DX5150]
MSP430F6659AIZWQ [DX5150]
MSP430F6720IPZ [DX3021]
MSP430F6721IPZ [DX3021]
MSP430F6723IPZ [DX3021]
MSP430F6724IPZ [DX3021]
MSP430F6725IPZ [DX3021]
MSP430F6726IPZ [DX3021]
MSP430F6730IPZ [DX3021]
MSP430F6731IPZ [DX3021]
MSP430F6733IPZ [DX3021]
MSP430F6734IPZ [DX3021]
MSP430F6735IPZ [DX3021]
MSP430F6736IPZ [DX3021]
MSP430F67471IPZ [DX3021]
MSP430F6747IPZ [DX3021]
MSP430F5659AIPZ [DX3021]
MSP430F6433AIPZ [DX3021]
MSP430F6433IPZ [DX3021]
MSP430F6434AIPZ [DX3021]
MSP430F6434IPZ [DX3021]
MSP430F6435AIPZ [DX3021]
MSP430F6435IPZ [DX3021]
MSP430F6436AIPZ [DX3021]
MSP430F6436IPZ [DX3021]
MSP430F6438AIPZ [DX3021]
MSP430F6438IPZ [DX3021]
MSP430F6458AIPZ [DX3021]
MSP430F6459AIPZ [DX3021]
MSP430F6630AIPZ [DX3021]
MSP430F6630IPZ [DX3021]
MSP430F6631AIPZ [DX3021]
MSP430F6631IPZ [DX3021]
MSP430F6632AIPZ [DX3021]
MSP430F6632IPZ [DX3021]
MSP430F6633AIPZ [DX3021]
MSP430F6633IPZ [DX3021]
MSP430F6634AIPZ [DX3021]
MSP430F6634IPZ [DX3021]
MSP430F6635AIPZ [DX3021]
MSP430F6635IPZ [DX3021]
MSP430F6636AIPZ [DX3021]
MSP430F6636IPZ [DX3021]
MSP430F6637AIPZ [DX3021]
MSP430F6637IPZ [DX3021]
MSP430F6638AIPZ [DX3021]
MSP430F6638IPZ [DX3021]
MSP430F6658AIPZ [DX3021]
MSP430F6659AIPZ [DX3021]
MSP430F6720IPN [DX3016]
MSP430F6721IPN [DX3016]
MSP430F6723IPN [DX3016]
MSP430F6724IPN [DX3016]
MSP430F6725IPN [DX3016]
MSP430F6726IPN [DX3016]
MSP430F6730IPN [DX3016]
MSP430F6731IPN [DX3016]
MSP430F6733IPN [DX3016]
MSP430F6734IPN [DX3016]
MSP430F6735IPN [DX3016]
MSP430F6736IPN [DX3016]
MSP430F67471IPEU [DX3032]
MSP430F6747IPEU [DX3032]
MSP430F67481IPEU [DX3032]

MSP430F67481IPZ [DX3021]
MSP430F6748IPZ [DX3021]
MSP430F67491IPZ [DX3021]
MSP430F6749IPZ [DX3021]
MSP430F67621IPZ [DX3021]
MSP430F67641IPZ [DX3021]
MSP430F67671IPZ [DX3021]
MSP430F6767IPZ [DX3021]
MSP430F67681IPZ [DX3021]
MSP430F6768IPZ [DX3021]
MSP430F67691IPZ [DX3021]
MSP430F6769IPZ [DX3021]
MSP430F67771IPZ [DX3021]
MSP430F6777IPZ [DX3021]
MSP430F67781IPZ [DX3021]
MSP430F6778IPZ [DX3021]
MSP430F67791IPZ [DX3021]
MSP430F6779IPZ [DX3021]
MSP430FE423@TQFP64 [DX3011]
MSP430FE4232@TQFP64 [DX3011]
MSP430FE423A@TQFP64 [DX3011]
MSP430FE4242@TQFP64 [DX3011]
MSP430FE425@TQFP64 [DX3011]
MSP430FE4252@TQFP64 [DX3011]
MSP430FE425A@TQFP64 [DX3011]
MSP430FE427@TQFP64 [DX3011]
MSP430FE4272@TQFP64 [DX3011]
MSP430FE427A@TQFP64 [DX3011]
MSP430FG4250@SSOP48 [DX1028]
MSP430FG4260@SSOP48 [DX1028]
MSP430FG4270@SSOP48 [DX1028]
MSP430FG437@TQFP80 [DX3016]
MSP430FG438@TQFP80 [DX3016]
MSP430FG439@TQFP80 [DX3016]
MSP430FG4616IPZR@TQFP100 [DX3021]
MSP430FG4617IPZ@TQFP100 [DX3021]
MSP430FG4617IPZR@TQFP100 [DX3021]
MSP430FG4618IPZ@TQFP100 [DX3021]
MSP430FG4618IPZR@TQFP100 [DX3021]
MSP430FG4619IPZ@TQFP100 [DX3021]
MSP430FG4619IPZR@TQFP100 [DX3021]
MSP430FG477@LQFP80 [DX3016]
MSP430FG479@LQFP80 [DX3016]
MSP430FR5720IRGE [DX4012]
MSP430FR5721IRHA [DX4017]
MSP430FR5722IRGE [DX4012]
MSP430FR5723IRHA [DX4017]
MSP430FR5724IRGE [DX4012]
MSP430F6748IPEU [DX3032]
MSP430F67491IPEU [DX3032]
MSP430F6749IPEU [DX3032]
MSP430F67621IPN [DX3016]
MSP430F67641IPN [DX3016]
MSP430F67671IPEU [DX3032]
MSP430F6767IPEU [DX3032]
MSP430F67681IPEU [DX3032]
MSP430F6768IPEU [DX3032]
MSP430F67691IPEU [DX3032]
MSP430F6769IPEU [DX3032]
MSP430F67771IPEU [DX3032]
MSP430F6777IPEU [DX3032]
MSP430F67781IPEU [DX3032]
MSP430F6778IPEU [DX3032]
MSP430F67791IPEU [DX3032]
MSP430F6779IPEU [DX3032]
MSP430FE423@QFN64 [DX4023]
MSP430FE4232@QFN64 [DX4023]
MSP430FE423A@QFN64 [DX4023]
MSP430FE4242@QFN64 [DX4023]
MSP430FE425@QFN64 [DX4023]
MSP430FE4252@QFN64 [DX4023]
MSP430FE425A@QFN64 [DX4023]
MSP430FE427@QFN64 [DX4023]
MSP430FE4272@QFN64 [DX4023]
MSP430FE427A@QFN64 [DX4023]
MSP430FG4250@QFN48 [DX4021]
MSP430FG4260@QFN48 [DX4021]
MSP430FG4270@QFN48 [DX4021]
MSP430FG437@TQFP100 [DX3021]
MSP430FG438@TQFP100 [DX3021]
MSP430FG439@TQFP100 [DX3021]
MSP430FG4616IPZ@TQFP100 [DX3021]
MSP430FG478@LQFP80 [DX3016]
MSP430FR5720IPW [DX1001]
MSP430FR5721IDA [DX1027]
MSP430FR5722IPW [DX1001]
MSP430FR5723IDA [DX1027]
MSP430FR5724IPW [DX1001]
MSP430FR5725IDA [DX1027]

MSP430FR5725IRHA [DX4017]
MSP430FR5726IPW [DX1001]
MSP430FR5726IRGE [DX4012]
MSP430FR5727IDA [DX1027]
MSP430FR5727IRHA [DX4017]
MSP430FR5728IPW [DX1001]
MSP430FR5728IRGE [DX4012]
MSP430FR5729IDA [DX1027]
MSP430FR5729IRHA [DX4017]
MSP430FR5730IPW [DX1001]
MSP430FR5730IRGE [DX4012]
MSP430FR5731IDA [DX1027]
MSP430FR5731IRHA [DX4017]
MSP430FR5732IPW [DX1001]
MSP430FR5732IRGE [DX4012]
MSP430FR5733IDA [DX1027]
MSP430FR5733IRHA [DX4017]
MSP430FR5734IPW [DX1001]
MSP430FR5734IRGE [DX4012]
MSP430FR5735IDA [DX1027]
MSP430FR5735IRHA [DX4017]
MSP430FR5736IPW [DX1001]
MSP430FR5736IRGE [DX4012]
MSP430FR5737IDA [DX1027]
MSP430FR5737IRHA [DX4017]
MSP430FR5738IPW [DX1001]
MSP430FR5738IRGE [DX4012]
MSP430FR5739IDA [DX1027]
MSP430FR5739IRHA [DX4017]
MSP430FR5949@QFN40 [DX4017]
MSP430FR5969IRGZ [DX4021]
MSP430FW423@TQFP64 [DX3011]
MSP430FW425@TQFP64 [DX3011]
MSP430FW427@TQFP64 [DX3011]
MSP430FW428@TQFP64 [DX3011]
MSP430FW429@TQFP64 [DX3011]
MSP430G2001IN [DX0001]
MSP430G2001IPW@TSSOP14 [DX1000]
MSP430G2001IRSA@QFN16 [DX4010]
MSP430G2001TN [DX0001]
MSP430G2001TPW@TSSOP14 [DX1000]
MSP430G2001TRSA@QFN16 [DX4010]
MSP430G2002IN [DX0001]
MSP430G2002IPW14@TSSOP14 [DX1000]
MSP430G2002IPW20@TSSOP20 [DX1001]
MSP430G2002IRSA@QFN16 [DX4010]
MSP430G2011IN [DX0001]
MSP430G2011IPW@TSSOP14 [DX1000]
MSP430G2011IRSA@QFN16 [DX4010]
MSP430G2011TN [DX0001]
MSP430G2011TPW@TSSOP14 [DX1000]
MSP430G2011TRSA@QFN16 [DX4010]
MSP430G2012IN [DX0001]
MSP430G2012IPW14 [DX1000]
MSP430G2012IPW20 [DX1001]
MSP430G2012IRSA [DX4010]
MSP430G2013IN20 [DX0001]
MSP430G2013IPW20 [DX1001]
MSP430G2013IPW28 [DX1001]
MSP430G2013IRH32 [DX4015]
MSP430G2021IN [DX0001]
MSP430G2021IPW@TSSOP14 [DX1000]
MSP430G2021IRSA@QFN16 [DX4010]
MSP430G2021TN [DX0001]
MSP430G2021TPW@TSSOP14 [DX1000]
MSP430G2021TRSA@QFN16 [DX4010]
MSP430G2031IN [DX0001]
MSP430G2031IPW@TSSOP14 [DX1000]
MSP430G2031IRSA@QFN16 [DX4010]
MSP430G2031TN [DX0001]
MSP430G2031TPW@TSSOP14 [DX1000]
MSP430G2031TRSA@QFN16 [DX4010]
MSP430G2032IN [DX0001]
MSP430G2032IPW14@TSSOP14 [DX1000]
MSP430G2032IPW20@TSSOP20 [DX1001]
MSP430G2032IRSA@QFN16 [DX4010]
MSP430G2052IN [DX0001]
MSP430G2052IPW14 [DX1000]
MSP430G2052IPW20 [DX1001]
MSP430G2052IRSA [DX4010]
MSP430G2053IN20 [DX0001]
MSP430G2053IPW20 [DX1001]
MSP430G2053IPW28 [DX1001]
MSP430G2053IRH32 [DX4015]
MSP430G2101IN [DX0001]
MSP430G2101IPW@TSSOP14 [DX1000]
MSP430G2101IRSA@QFN16 [DX4010]
MSP430G2101TN [DX0001]
MSP430G2101TPW@TSSOP14 [DX1000]
MSP430G2101TRSA@QFN16 [DX4010]
MSP430G2102IN [DX0001]

MSP430G2102IPW14@TSSOP14 [DX1000]
MSP430G2102IPW20@TSSOP20 [DX1001]
MSP430G2102IRSA@QFN16 [DX4010]
MSP430G2111IN [DX0001]
MSP430G2111IPW@TSSOP14 [DX1000]
MSP430G2111IRSA@QFN16 [DX4010]
MSP430G2111TN [DX0001]
MSP430G2111TPW@TSSOP14 [DX1000]
MSP430G2111TRSA@QFN16 [DX4010]
MSP430G2112IN [DX0001]
MSP430G2112IPW14 [DX1000]
MSP430G2112IPW20 [DX1001]
MSP430G2112IRSA [DX4010]
MSP430G2113IN20 [DX0001]
MSP430G2113IPW20 [DX1001]
MSP430G2113IPW28 [DX1001]
MSP430G2113IRH32 [DX4015]
MSP430G2121IN [DX0001]
MSP430G2121IPW@TSSOP14 [DX1000]
MSP430G2121IRSA@QFN16 [DX4010]
MSP430G2121TN [DX0001]
MSP430G2121TPW@TSSOP14 [DX1000]
MSP430G2121TRSA@QFN16 [DX4010]
MSP430G2131IN [DX0001]
MSP430G2131IPW@TSSOP14 [DX1000]
MSP430G2131IRSA@QFN16 [DX4010]
MSP430G2131TN [DX0001]
MSP430G2131TPW@TSSOP14 [DX1000]
MSP430G2131TRSA@QFN16 [DX4010]
MSP430G2132IN [DX0001]
MSP430G2132IPW14@TSSOP14 [DX1000]
MSP430G2132IPW20@TSSOP20 [DX1001]
MSP430G2132IRSA@QFN16 [DX4010]
MSP430G2152IN [DX0001]
MSP430G2152IPW14 [DX1000]
MSP430G2152IPW20 [DX1001]
MSP430G2152IRSA [DX4010]
MSP430G2153IN20 [DX0001]
MSP430G2153IPW20 [DX1001]
MSP430G2153IPW28 [DX1001]
MSP430G2153IRH32 [DX4015]
MSP430G2201IN [DX0001]
MSP430G2201IPW@TSSOP14 [DX1000]
MSP430G2201IRSA@QFN16 [DX4010]
MSP430G2201TN [DX0001]
MSP430G2201TPW@TSSOP14 [DX1000]
MSP430G2201TRSA@QFN16 [DX4010]
MSP430G2202IN [DX0001]
MSP430G2202IPW14@TSSOP14 [DX1000]
MSP430G2202IPW20@TSSOP20 [DX1001]
MSP430G2202IRSA@QFN16 [DX4010]
MSP430G2203IN20 [DX0001]
MSP430G2203IPW20 [DX1001]
MSP430G2203IPW28 [DX1001]
MSP430G2203IRH32 [DX4015]
MSP430G2210ID [DX1016]
MSP430G2210IDR [DX1016]
MSP430G2211IN [DX0001]
MSP430G2211IPW@TSSOP14 [DX1000]
MSP430G2211IRSA@QFN16 [DX4010]
MSP430G2211TN [DX0001]
MSP430G2211TPW@TSSOP14 [DX1000]
MSP430G2211TRSA@QFN16 [DX4010]
MSP430G2212IN [DX0001]
MSP430G2212IPW14 [DX1000]
MSP430G2212IPW20 [DX1001]
MSP430G2212IRSA [DX4010]
MSP430G2213IN20 [DX0001]
MSP430G2213IPW20 [DX1001]
MSP430G2213IPW28 [DX1001]
MSP430G2213IRH32 [DX4015]
MSP430G2221IN [DX0001]
MSP430G2221IPW@TSSOP14 [DX1000]
MSP430G2221IRSA@QFN16 [DX4010]
MSP430G2221TN [DX0001]
MSP430G2221TPW@TSSOP14 [DX1000]
MSP430G2221TRSA@QFN16 [DX4010]
MSP430G2230ID [DX1016]
MSP430G2230IDR [DX1016]
MSP430G2231IN [DX0001]
MSP430G2231IPW@TSSOP14 [DX1000]
MSP430G2231IRSA@QFN16 [DX4010]
MSP430G2231TN [DX0001]
MSP430G2231TPW@TSSOP14 [DX1000]
MSP430G2231TRSA@QFN16 [DX4010]
MSP430G2232IN [DX0001]
MSP430G2232IPW14@TSSOP14 [DX1000]
MSP430G2232IPW20@TSSOP20 [DX1001]

MSP430G2232IRSA@QFN16 [DX4010]
MSP430G2233IN20 [DX0001]
MSP430G2233IPW20 [DX1001]
MSP430G2233IPW28 [DX1001]
MSP430G2233IRH32 [DX4015]
MSP430G2252IN [DX0001]
MSP430G2252IPW14 [DX1000]
MSP430G2252IPW20 [DX1001]
MSP430G2252IRSA [DX4010]
MSP430G2253IN20 [DX0001]
MSP430G2253IPW20 [DX1001]
MSP430G2253IPW28 [DX1001]
MSP430G2253IRH32 [DX4015]
MSP430G2253IRHS [DX4030]
MSP430G2302IN [DX0001]
MSP430G2302IPW14@TSSOP14 [DX1000]
MSP430G2302IPW20@TSSOP20 [DX1001]
MSP430G2302IRSA@QFN16 [DX4010]
MSP430G2303IN20 [DX0001]
MSP430G2303IPW20 [DX1001]
MSP430G2303IPW28 [DX1001]
MSP430G2303IRH32 [DX4015]
MSP430G2312IN [DX0001]
MSP430G2312IPW14 [DX1000]
MSP430G2312IPW20 [DX1001]
MSP430G2312IRSA [DX4010]
MSP430G2313IN20 [DX0001]
MSP430G2313IPW20 [DX1001]
MSP430G2313IPW28 [DX1001]
MSP430G2313IRH32 [DX4015]
MSP430G2332IN [DX0001]
MSP430G2332IPW14@TSSOP14 [DX1000]
MSP430G2332IPW20@TSSOP20 [DX1001]
MSP430G2332IRSA@QFN16 [DX4010]
MSP430G2333IN20 [DX0001]
MSP430G2333IPW20 [DX1001]
MSP430G2333IPW28 [DX1001]
MSP430G2333IRH32 [DX4015]
MSP430G2344IDA [DX1027]
MSP430G2344IN [DX0001]
MSP430G2344IRHA [DX4017]
MSP430G2344IYFF [BBBB]
MSP430G2352IN [DX0001]
MSP430G2352IPW14 [DX1000]
MSP430G2352IPW20 [DX1001]
MSP430G2352IRSA [DX4010]
MSP430G2353IN20 [DX0001]
MSP430G2353IPW20 [DX1001]
MSP430G2353IPW28 [DX1001]
MSP430G2353IRH32 [DX4015]
MSP430G2402IN [DX0001]
MSP430G2402IPW14@TSSOP14 [DX1000]
MSP430G2402IPW20@TSSOP20 [DX1001]
MSP430G2402IRSA@QFN16 [DX4010]
MSP430G2403IN20 [DX0001]
MSP430G2403IPW20 [DX1001]
MSP430G2403IPW28 [DX1001]
MSP430G2403IRH32 [DX4015]
MSP430G2412IN [DX0001]
MSP430G2412IPW14 [DX1000]
MSP430G2412IPW20 [DX1001]
MSP430G2412IRSA [DX4010]
MSP430G2413IN20 [DX0001]
MSP430G2413IPW20 [DX1001]
MSP430G2413IPW28 [DX1001]
MSP430G2413IRH32 [DX4015]
MSP430G2432IN [DX0001]
MSP430G2432IPW14@TSSOP14 [DX1000]
MSP430G2432IPW20@TSSOP20 [DX1001]
MSP430G2432IRSA@QFN16 [DX4010]
MSP430G2433IN20 [DX0001]
MSP430G2433IPW20 [DX1000]
MSP430G2433IPW28 [DX1001]
MSP430G2433IRH32 [DX4015]
MSP430G2452IN [DX0001]
MSP430G2452IPW14 [DX1000]
MSP430G2452IPW20 [DX1000]
MSP430G2452IRSA [DX4010]
MSP430G2453IN20 [DX0001]
MSP430G2453IPW20 [DX1000]
MSP430G2453IPW28 [DX1001]
MSP430G2453IRH32 [DX4015]
MSP430G2503IN20 [DX0001]
MSP430G2503IPW20 [DX1001]
MSP430G2503IPW28 [DX1001]
MSP430G2503IRH32 [DX4015]
MSP430G2513IN20 [DX0001]

MSP430G2513IPW20 [DX1001]
MSP430G2513IPW28 [DX1001]
MSP430G2513IRH32 [DX4015]
MSP430G2533IN20 [DX0001]
MSP430G2533IPW20 [DX1000]
MSP430G2533IPW28 [DX1001]
MSP430G2533IRH32 [DX4015]
MSP430G2544IDA [DX1027]
MSP430G2544IN [DX0001]
MSP430G2544IRHA [DX4017]
MSP430G2544IYFF [BBBB]
MSP430G2553IN20 [DX0001]
MSP430G2553IPW20 [DX1000]
MSP430G2553IPW28 [DX1001]
MSP430G2553IRH32 [DX4015]
MSP430G2744IDA [DX1027]
MSP430G2744IN [DX0001]
MSP430G2744IRHA [DX4017]
MSP430G2744IYFF [BBBB]
MSP430G2755IDA [DX1027]
MSP430G2755IN [DX0001]
MSP430G2755IRHA [DX4017]
MSP430G2755IYFF [BBBB]
MSP430G2855IDA [DX1027]
MSP430G2855IN [DX0001]
MSP430G2855IRHA [DX4017]
MSP430G2855IYFF [BBBB]
MSP430G2955IDA [DX1027]
MSP430G2955IN [DX0001]
MSP430G2955IRHA [DX4017]
MSP430G2955IYFF [BBBB]
MSP430V103@QFN64 [DX4023]
MSP430V103@QFP64 [DX3011]
TM4C1230C3PM@LQFP64 [DX3057-9]
TM4C1230D5PM@LQFP64 [DX3057-9]
TM4C1230E6PM@LQFP64 [DX3057-9]
TM4C1230H6PM@LQFP64 [DX3057-9]
TM4C1231C3PM@LQFP64 [DX3057-9]
TM4C1231D5PM@LQFP64 [DX3057-9]
TM4C1231D5PZ@LQFP10 [DX3043-5]
TM4C1231E6PM@LQFP64 [DX3057-9]
TM4C1231E6PZ@LQFP10 [DX3043-5]
TM4C1231H6PGE@LQFP144 [DX3051-3]
TM4C1231H6PM@LQFP64 [DX3057-9]
TM4C1231H6PZ@LQFP10 [DX3043-5]
TM4C1232C3PM@LQFP64 [DX3057-9]
TM4C1232D5PM@LQFP64 [DX3057-9]
TM4C1232E6PM@LQFP64 [DX3057-9]
TM4C1232H6PM@LQFP64 [DX3057-9]
TM4C1233C3PM@LQFP64 [DX3057-9]
TM4C1233D5PM@LQFP64 [DX3057-9]
TM4C1233D5PZ@LQFP10 [DX3043-5]
TM4C1233E6PM@LQFP64 [DX3057-9]
TM4C1233E6PZ@LQFP10 [DX3043-5]
TM4C1233H6PGE@LQFP144 [DX3051-3]
TM4C1233H6PM@LQFP64 [DX3057-9]
TM4C1233H6PZ@LQFP10 [DX3043-5]
TM4C1236D5PM@LQFP64 [DX3057-9]
TM4C1236E6PM@LQFP64 [DX3057-9]
TM4C1236H6PM@LQFP64 [DX3057-9]
TM4C1237D5PM@LQFP64 [DX3057-9]
TM4C1237D5PZ@LQFP10 [DX3043-5]
TM4C1237E6PM@LQFP64 [DX3057-9]
TM4C1237E6PZ@LQFP10 [DX3043-5]
TM4C1237H6PGE@LQFP144 [DX3051-3]
TM4C1237H6PM@LQFP64 [DX3057-9]
TM4C1237H6PZ@LQFP10 [DX3043-5]
TM4C123AE6PM@LQFP64 [DX3057-9]
TM4C123AH6PM@LQFP64 [DX3057-9]
TM4C123BE6PM@LQFP64 [DX3057-9]
TM4C123BE6PZ@LQFP10 [DX3043-5]
TM4C123BH6PGE@LQFP144 [DX3051-3]
TM4C123BH6PM@LQFP64 [DX3057-9]
TM4C123BH6PZ@LQFP10 [DX3043-5]
TM4C123FE6PM@LQFP64 [DX3057-9]
TM4C123FH6PM@LQFP64 [DX3057-9]
TM4C123GE6PM@LQFP64 [DX3057-9]
TM4C123GE6PZ@LQFP10 [DX3043-5]
TM4C123GH6PGE@LQFP144 [DX3051-3]
TM4C123GH6PM@LQFP64 [DX3057-9]
TM4C123GH6PZ@LQFP10 [DX3043-5]
TM4C1290NCPDT@LQFP128 [DX3030]
TM4C1292NCPDT@LQFP128 [DX3030]
TM4C1294KCPDT@LQFP128 [DX3030]
TM4C1294NCPDT@LQFP128 [DX3030]
TM4C129CNCPDT@LQFP128 [DX3030]
TM4C129DNCPDT@LQFP128 [DX3030]
TM4C129EKCPDT@LQFP128 [DX3030]
TM4C129ENCPDT@LQFP128 [DX3030]
TMS320E14@PLCC68 [DX2068]
TMS320E15 [DX0001]
TMS320E15@PLCC44 [DX2044]
TMS320E17 [DX0001]
TMS320E17@PLCC44 [DX2044]
TMS320E25@PLCC68 [DX2068]
TMS320F2801@BGA100 [DX5106]

TMS320F2801@LQFP100 [DX3043]
TMS320F28015@LQFP100 [DX3043]
TMS320F2802@LQFP100 [DX3043]
TMS320F28020@TSSOP38 [DX1027]
TMS320F280200@TSSOP38 [DX1027]
TMS320F28021@TSSOP38 [DX1027]
TMS320F28022@TSSOP38 [DX1027]
TMS320F28023@TSSOP38 [DX1027]
TMS320F280230@TSSOP38 [DX1027]
TMS320F28026@TSSOP38 [DX1027]
TMS320F28027@TSSOP38 [DX1027]
TMS320F28030@LQFP80 [DX3016]
TMS320F28031@LQFP80 [DX3016]
TMS320F28032@LQFP80 [DX3016]
TMS320F28033@LQFP80 [DX3016]
TMS320F28034@LQFP80 [DX3016]
TMS320F28035@LQFP64 [DX3011]
TMS320F28035@QFN56 [DX4089]
TMS320F28044@LQFP100 [DX3043]
TMS320F2806@LQFP100 [DX3043]
TMS320F28062@LQFP80 [DX3016]
TMS320F28063@LQFP80 [DX3016]
TMS320F28064@LQFP80 [DX3016]
TMS320F28065@LQFP80 [DX3016]
TMS320F28066@LQFP80 [DX3016]
TMS320F28067@LQFP80 [DX3016]
TMS320F28068@LQFP80 [DX3016]
TMS320F28069@LQFP80 [DX3016]
TMS320F2808@LQFP100 [DX3043]
TMS320F2809@LQFP100 [DX3043]
TMS320F2812@LQFP176 [DX3083]
TMS320F28234@LQFP176 [DX3083]
TMS320LF2401A@LQFP32 [DX3001]
TMS320LF2403A@LQFP64 [DX3057-2]
TMS320LF2407A@LQFP144 [DX3051-1]
TMS320P15 [DX0001]
TMS320P17 [DX0001]
TMS320P25@PLCC68 [DX2068]
TMS37122A [DX1000]
TPS61177@QFN20(Left Down) [DX4094]
TPS65143@BGA56 [DX5259]
TPS65177@QFN40 [DX4017]
TPS65177@QFN40(left down) [DX4017]
TPS65178@QFN48 [DX4043]
TPS65836RKPR@QFN40 [DX4039]
UCD9222RGZT [DX4021-4]
UCD9224RGZT [DX4021-4]
X430F46161IPZR@TQFP100 [DX3021]
TMS320F28015@BGA100 [DX5106]
TMS320F2802@BGA100 [DX5106]
TMS320F28020@LQFP48 [DX3007]
TMS320F280200@LQFP48 [DX3007]
TMS320F28021@LQFP48 [DX3007]
TMS320F28022@LQFP48 [DX3007]
TMS320F28023@LQFP48 [DX3007]
TMS320F280230@LQFP48 [DX3007]
TMS320F28026@LQFP48 [DX3007]
TMS320F28027@LQFP48 [DX3007]
TMS320F28030@LQFP64 [DX3011]
TMS320F28031@LQFP64 [DX3011]
TMS320F28032@LQFP64 [DX3011]
TMS320F28033@LQFP64 [DX3011]
TMS320F28034@LQFP64 [DX3011]
TMS320F28034@QFN56 [DX4089]
TMS320F28035@LQFP80 [DX3016]
TMS320F28044@BGA100 [DX5106]
TMS320F2806@BGA100 [DX5106]
TMS320F28062@LQFP100 [DX3043]
TMS320F28063@LQFP100 [DX3043]
TMS320F28064@LQFP100 [DX3043]
TMS320F28065@LQFP100 [DX3043]
TMS320F28066@LQFP100 [DX3043]
TMS320F28067@LQFP100 [DX3043]
TMS320F28068@LQFP100 [DX3043]
TMS320F28069@LQFP100 [DX3043]
TMS320F2808@BGA100 [DX5106]
TMS320F2809@BGA100 [DX5106]
TMS320F2811@LQFP128 [DX3030]
TMS320F28232@LQFP176 [DX3083]
TMS320F28335@LQFP176 [DX3083]
TMS320LF2402A@PQFP64 [DX3068-1]
TMS320LF2406A@LQFP100 [DX3043-1]
TMS320P14@PLCC68 [DX2068]
TMS320P15@PLCC44 [DX2044]
TMS320P17@PLCC44 [DX2044]
TMS37122 [DX1000]
TPS61177@QFN20 [DX4094]
TPS65168@QFN40 [DX4039]
TPS65835RKPR@QFN40 [DX4039]
UCD9222RGZR [DX4021-4]
UCD9224RGZR [DX4021-4]
X430F46161IPZ@TQFP100 [DX3021]
X430F4616IPZ@TQFP100 [DX3021]

X430F4616IPZR@TQFP100 [DX3021]
X430F46171IPZR@TQFP100 [DX3021]
X430F4617IPZR@TQFP100 [DX3021]
X430F46181IPZR@TQFP100 [DX3021]
X430F4618IPZR@TQFP100 [DX3021]
X430F46191IPZR@TQFP100 [DX3021]
X430F4619IPZR@TQFP100 [DX3021]
X430FG4616IPZR@TQFP100 [DX3021]
X430FG4617IPZR@TQFP100 [DX3021]
X430FG4618IPZR@TQFP100 [DX3021]
X430FG4619IPZR@TQFP100 [DX3021]
XMS430FR5720IRGE [DX4012]
XMS430FR5721IRHA [DX4017]
XMS430FR5722IRGE [DX4012]
XMS430FR5723IRHA [DX4017]
XMS430FR5724IRGE [DX4012]
XMS430FR5725IRHA [DX4017]
XMS430FR5726IRGE [DX4012]
XMS430FR5727IRHA [DX4017]
XMS430FR5728IRGE [DX4012]
XMS430FR5729IRHA [DX4017]
XMS430FR5730IRGE [DX4012]
XMS430FR5731IRHA [DX4017]
XMS430FR5732IRGE [DX4012]
XMS430FR5733IRHA [DX4017]
XMS430FR5734IRGE [DX4012]
XMS430FR5735IRHA [DX4017]
XMS430FR5736IRGE [DX4012]
XMS430FR5737IRHA [DX4017]
XMS430FR5738IRGE [DX4012]
XMS430FR5739IRHA [DX4017]
X430F46171IPZ@TQFP100 [DX3021]
X430F4617IPZ@TQFP100 [DX3021]
X430F46181IPZ@TQFP100 [DX3021]
X430F4618IPZ@TQFP100 [DX3021]
X430F46191IPZ@TQFP100 [DX3021]
X430F4619IPZ@TQFP100 [DX3021]
X430FG4616IPZ@TQFP100 [DX3021]
X430FG4617IPZ@TQFP100 [DX3021]
X430FG4618IPZ@TQFP100 [DX3021]
X430FG4619IPZ@TQFP100 [DX3021]
XMS430FR5720IPW [DX1001]
XMS430FR5721IDA [DX1027]
XMS430FR5722IPW [DX1001]
XMS430FR5723IDA [DX1027]
XMS430FR5724IPW [DX1001]
XMS430FR5725IDA [DX1027]
XMS430FR5726IPW [DX1001]
XMS430FR5727IDA [DX1027]
XMS430FR5728IPW [DX1001]
XMS430FR5729IDA [DX1027]
XMS430FR5730IPW [DX1001]
XMS430FR5731IDA [DX1027]
XMS430FR5732IPW [DX1001]
XMS430FR5733IDA [DX1027]
XMS430FR5734IPW [DX1001]
XMS430FR5735IDA [DX1027]
XMS430FR5736IPW [DX1001]
XMS430FR5737IDA [DX1027]
XMS430FR5738IPW [DX1001]
XMS430FR5739IDA [DX1027]
XMS430FR5969IRGZ [DX4021]

TI-CUSTOMER

MICROCONTROLLER

LM3S1811@LQFP100 [DX3043]
LM3S1911@TQFP100 [DX3021]
LM3S1911@TQFP100(TONGCHI) [DX3021]
LM3S1911@BGA108(bosen) [DX5107]

TMC

E(E)PROM/FRAM/NVRAM

24A01 [DX0001]
24A01@TSSOP8 [DX1059]
24A01@SOIC8 [DX1045]
24A02 [DX0001]

24A02@SOIC8 [DX1045]
24A02@TSSOP8 [DX1059]
24A04 [DX0001]
24A04@SOIC8 [DX1045]
24A04@TSSOP8 [DX1059]
24A08 [DX0001]
24A08@SOIC8 [DX1045]
24A08@TSSOP8 [DX1059]
24A16 [DX0001]
24A16@SOIC8 [DX1045]
24A16@TSSOP8 [DX1059]
93LC46(08bit) [DX0001]
93LC46(08bit)@SOIC8 [DX1045]
93LC46(08bit)@TSSOP8 [DX1059]
93LC46(16bit) [DX0001]
93LC46(16bit)@SOIC8 [DX1045]
93LC46(16bit)@TSSOP8 [DX1059]
93LC56(08bit) [DX0001]
93LC56(08bit)@SOIC8 [DX1045]
93LC56(08bit)@TSSOP8 [DX1059]
93LC56(16bit) [DX0001]
93LC56(16bit)@SOIC8 [DX1045]
93LC56(16bit)@TSSOP8 [DX1059]
93LC57 [DX0001]
93LC57@SOIC8 [DX1045]
93LC57@TSSOP8 [DX1059]
93LC66(08bit) [DX0001]
93LC66(08bit)@SOIC8 [DX1045]
93LC66(08bit)@TSSOP8 [DX1059]
93LC66(16bit) [DX0001]
93LC66(16bit)@SOIC8 [DX1045]
93LC66(16bit)@TSSOP8 [DX1059]
93LC86(08bit) [DX0001]
93LC86(08bit)@SOIC8 [DX1045]
93LC86(08bit)@TSSOP8 [DX1059]
93LC86(16bit) [DX0001]
93LC86(16bit)@SOIC8 [DX1045]
93LC86(16bit)@TSSOP8 [DX1059]

TOPRO

MICROCONTROLLER

TP2804H [DX0001]
TP2804H@PLCC44 [DX2044]
TP2804H@TQFP44 [DX3005]
TP2804L [DX0001]
TP2804L@PLCC44 [DX2044]
TP2804L@TQFP44 [DX3005]
TP2808H [DX0001]
TP2808H@PLCC44 [DX2044]
TP2808H@TQFP44 [DX3005]
TP2808L [DX0001]
TP2808L@PLCC44 [DX2044]
TP2808L@TQFP44 [DX3005]
TP2818H [DX0001]
TP2818H@PLCC44 [DX2044]
TP2818H@TQFP44 [DX3005]
TP2818L [DX0001]
TP2818L@PLCC44 [DX2044]
TP2818L@TQFP44 [DX3005]
TP2851 [DX0001]
TP2851@PLCC44 [DX2044]
TP2851@TQFP44 [DX3005]
TP2852 [DX0001]
TP2852@PLCC44 [DX2044]
TP2852@TQFP44 [DX3005]

TOPSCOMM

MICROCONTROLLER

R7F0C003M2DFB@QFP80 [DX3016]
R7F0C004M2DFB@QFP80 [DX3016]
TCC081F@QFN32 [DX4015-9]

TOSHIBA

E(E)PROM/FRAM/NVRAM

TC541000AF@PLCC32 [DX0001]
TC541000AP [DX0001]
TC541001AF@PLCC32 [DX0001]
TC541001AP [DX0001]
TC54256AF [DX0001]
TC54256AF@SOIC28
TC54256AP [DX0001]
TC54256AP@SOIC28
TC544000P [DX0001]
TC54512AF [DX0001]
TC54512AP [DX0001]
TC571000 [DX0001]
TC571000AD [DX0001]
TC571000D [DX0001]
TC571001AD [DX0001]
TC571001D [DX0001]
TC571024D [DX0001]
TC57256 [DX0001]
TC57256A [DX0001]
TC57256AD [DX0001]
TC57256ADI [DX0001]
TC57256D [DX0001]
TC574000D [DX0001]
TC574096D [DX0001]
TC574200D [DX0001]
TC57512 [DX0001]
TC57512AD [DX0001]
TC578200D [DX0001]
TC57H1000AD [DX0001]
TC57H1001AD [DX0001]
TC57H256D [DX0001]
TC58128AFT@TSOP48 [DX1004]
TC58256AFT@TSOP48 [DX1004]
TC58512FT@TSOP48 [DX1004]
TC58BVG0S3HTA00@TSOP48 [DX1004-3]
TC58BVG1S3HTA00@TSOP48 [DX1004-3]
TC58DVG02A1FT00@TSOP48 [DX1004]
TC58DVG02D5TA00@TSOP48 [DX1004-1]
TC58DVG3S0ETA00@TSOP48 [DX1004-1]
TC58DVM72A1FT00@TSOP48 [DX1004]
TC58DVM72A1TG00@TSOP48 [DX1004]
TC58DVM82A1FT00@TSOP48 [DX1004]
TC58DVM92A1FT00@TSOP48 [DX1004]
TC58DVM92A5TA00@TSOP48 [DX1004]
TC58DYG02D5BAI4@FBGA63 [DX5046]
TC58F400@PSOP44 [DX1014]
TC58F400@TSOP48 [DX1004]
TC58F401@PSOP44 [DX1014]
TC58F401@TSOP48 [DX1004]
TC58FVB004FT@TSOP40 [DX1006]
TC58FVB008FT@TSOP40 [DX1006]
TC58FVB016FT@TSOP40 [DX1006]
TC58FVB160AFT@TSOP48 [DX1004]
TC58FVB160AXB@TFBGA48 [DX5002]
TC58FVB160FT@TSOP48 [DX1004]
TC58FVB321FT@TSOP48 [DX1004]
TC58FVB321XB@TFBGA56 [DX5046]
TC58FVB400F@PSOP44 [DX1014]
TC58FVB400FT@TSOP48 [DX1004]
TC58FVB641FT@TSOP48 [DX1004]
TC58FVB641XB@TFBGA63 [DX5046]
TC58FVB800F@PSOP44 [DX1014]
TC58FVB800FT@TSOP48 [DX1004]
TC58FVM5B2AFT@TSOP48 [DX1004]
TC58FVM5B2ATG@TSOP48 [DX1004]
TC58FVM5B2AXB@TFBGA56 [DX5005]
TC58FVM5B2AXG@TFBGA56 [DX5005]
TC58FVM5B3AFT@TSOP48 [DX1004]
TC58FVM5B3ATG@TSOP48 [DX1004]
TC58FVM5B3AXB@TFBGA56 [DX5005]
TC58FVM5B3AXG@TFBGA56 [DX5005]
TC58FVM5T2AFT@TSOP48 [DX1004]
TC58FVM5T2ATG@TSOP48 [DX1004]
TC58FVM5T2AXB@TFBGA56 [DX5005]
TC58FVM5T2AXG@TFBGA56 [DX5005]
TC58FVM5T3AFT@TSOP48 [DX1004]
TC58FVM5T3ATG@TSOP48 [DX1004]
TC58FVM5T3AXB@TFBGA56 [DX5005]
TC58FVM5T3AXG@TFBGA56 [DX5005]
TC58FVM6B2AFT@TSOP48 [DX1004]
TC58FVM6B2AXB@TFBGA63 [DX5005]
TC58FVM6B5BTG@TSOP48 [DX1004]
TC58FVM6B5BXG@TFBGA56 [DX5005]
TC58FVM6T2AFT@TSOP48 [DX1004]
TC58FVM6T2AXB@TFBGA63 [DX5005]

TC58FVM6T5BTG@TSOP48 [DX1004]
TC58FVM6T5BXG@TFBGA56 [DX5005]
TC58FVM7B2AFT@TSOP56 [DX1055]
TC58FVM7B2AT@TSOP56 [DX1011]
TC58FVM7B5BTG@TSOP56 [DX1055]
TC58FVM7B5BXG@FBGA80 [DX5005]
TC58FVM7T2AFT@TSOP56 [DX1055]
TC58FVM7T5BTG@TSOP56 [DX1055]
TC58FVM7T5BXG@FBGA80 [DX5005]
TC58FVT004FT@TSOP40 [DX1006]
TC58FVT008FT@TSOP40 [DX1006]
TC58FVT016FT@TSOP40 [DX1006]
TC58FVT160AFT@TSOP48 [DX1004]
TC58FVT160AXB@TFBGA48 [DX5002]
TC58FVT160FT@TSOP48 [DX1004]
TC58FVT321FT@TSOP48 [DX1004]
TC58FVT321XB@TFBGA56 [DX5046]
TC58FVT400F@PSOP44 [DX1014]
TC58FVT400FT@TSOP48 [DX1004]
TC58FVT641FT@TSOP48 [DX1004]
TC58FVT641XB@TFBGA63 [DX5046]
TC58FVT800F@PSOP44 [DX1014]
TC58FVT800FT@TSOP48 [DX1004]
TC58FYB160FT@TSOP48 [DX1004]
TC58FYT160FT@TSOP48 [DX1004]
TC58NVG0ABEBAI4@BGA63 [DX5005]
TC58NVG0S3AFT05@TSOP48 [DX1004]
TC58NVG0S3CTA00@TSOP48 [DX1004]
TC58NVG0S3EBAI4@FBGA63 [DX5046]
TC58NVG0S3EBAI7@FBGA63 [DX5046]
TC58NVG0S3ETA00@TSOP48 [DX1004-1]
TC58NVG0S3ETAI0@TSOP48 [DX1004-1]
TC58NVG0S3ETAIB@TSOP48 [DX1004-1]
TC58NVG0S3HTA00@TSOP48 [DX1004-3]
TC58NVG1S3EBAI4@FBGA63 [DX5046]
TC58NVG1S3EBAI5@FBGA63 [DX5168]
TC58NVG1S3ETA00@TSOP48 [DX1004-3]
TC58NVG1S3ETAI0@TSOP48 [DX1004-1]
TC58NVG1S3HBAI4@FBGA63 [DX5046]
TC58NVG1S3HTA00@TSOP48 [DX1004-3]
TC58NVG1S3HTAI0@TSOP48 [DX1004-3]
TC58NVG2S0FTA00@TSOP48 [DX1004-1]
TC58NVG2S3EBAI5@FBAG63 [DX5168]
TC58NVG2S3ETA00@TSOP48 [DX1004-1]
TC58NVG2S3ETAI0@TSOP48 [DX1004-3]
TC58NVG3S0ETA00@TSOP48 [DX1004-1]
TC58NVG3S0FTA00@TSOP48 [DX1004-3]
TC58NVG4D2FTA00@TSOP48 [DX1004-1]
TC58NVM9S3EBAI4@FBGA63 [DX5046]
TC58NVM9S3ETA00@TSOP48 [DX1004-1]
TC58NYG0S3EBAI4@FBGA63 [DX5046]
TC58NYG1S3EBAI4@FBGA63 [DX5046]
TC58NYG1S3EBAI5@FBGA63 [DX5168]
TC58NYG2S3EBAI5@FBGA63 [DX5168]
TC89101(08bit) [DX0001]
TC89101(16bit) [DX0001]
TC89102(08bit) [DX0001]
TC89102(16bit) [DX0001]
TC89121 [DX0001]
TC89121@SOIC8 [DX1045]
TC89122 [DX0001]
TC89122@SOIC8 [DX1045]
TC97101 [DX0001]
TH50VPF5582ADSB@FBGA73 [DX5005]
TH50VPF5583ADSB@FBGA73 [DX5005]
TH50VPF5682CDSB@FBGA73 [DX5005]
TH50VPF5683CDSB@FBGA73 [DX5005]
TH50VPF5782AASB@FBGA73 [DX5057]
TH50VPF5783AASB@FBGA73 [DX5057]
TH50VPF6782AASB@FBGA73 [DX5057]
TH50VPF6783AASB@FBGA73 [DX5057]
TH50VSF1480AASB@FBGA65 [DX5057]
TH50VSF1481AASB@FBGA65 [DX5057]
TH50VSF2480AASB@FBGA65 [DX5057]
TH50VSF2481AASB@FBGA65 [DX5057]
TH50VSF2580AASB@FBGA69 [DX5057]
TH50VSF2581AASB@FBGA69 [DX5057]
TH50VSF2582AASB@FBGA69 [DX5057]

TH50VSF2582ADSB@FBGA73 [DX5005]
TH50VSF2582BDSB@FBGA73 [DX5005]
TH50VSF2583AASB@FBGA69 [DX5057]
TH50VSF2583ADSB@FBGA73 [DX5005]
TH50VSF2583BDSB@FBGA73 [DX5005]
TH50VSF2590AASB@FBGA69 [DX5001]
TH50VSF2682BDSB@FBGA73 [DX5005]
TH50VSF2683BDSB@FBGA73 [DX5005]
TH50VSF3580AASB@FBGA69 [DX5057]
TH50VSF3581AASB@FBGA69 [DX5057]
TH50VSF3582AASB@FBGA69 [DX5057]
TH50VSF3582BDSB@FBGA73 [DX5005]
TH50VSF3583AASB@FBGA69 [DX5057]
TH50VSF3583BDSB@FBGA73 [DX5005]
TH50VSF3680AASB@FBGA69 [DX5057]
TH50VSF3681AASB@FBGA69 [DX5057]
TH50VSF3682AASB@FBGA69 [DX5057]
TH50VSF3682BDSB@FBGA73 [DX5005]
TH50VSF3683AASB@FBGA69 [DX5057]
TH50VSF3683BDSB@FBGA73 [DX5005]
TH50VSF4682AASB@FBGA69 [DX5057]
TH50VSF4683AASB@FBGA69 [DX5057]
TH58BVG2S3HTAI0@TSOP48 [DX1004-3]
TH58DVG4S0ETAK0(1G)@TSOP48 [DX1004-1]
TH58DVG5S0ETAK0(1G)@TSOP48 [DX1004-1]
TH58NVG1S3AFT05@TSOP48 [DX1004]
TH58NVG4S0FBAID(256M)@FBGA63 [DX5235]
TH58NVG4S0FBAID@FBGA63 [DX5235]
TH58NVG5S0FTAK0(2G)@TSOP48 [DX1004-1]
THGBM2G6D2FBAI9(20M)@FBGA169 [DX5113-1]
THGBM2G6D2FBAI9(2G)@FBGA169 [DX5113-1]
THGBM2G7D4FBAI9(20M)@FBGA169 [DX5113-1]
THGBM2G7D4FBAI9(2G)@FBGA169 [DX5113-1]
THGBM2G8D8FBAI2(20M)@FBGA169 [DX5170-1]
THGBM2G8D8FBAI2(2G)@FBGA169 [DX5170-1]
THGBM2G8D8FBAIB(20M)@FBGA169 [DX5113-1]
THGBM2G8D8FBAIB(2G)@FBGA169 [DX5113-1]
THGBM3G5D1FBAIE(20M)@FBGA169 [DX5113-1]
THGBM3G5D1FBAIE(2G)@FBGA169 [DX5113-1]
THGBM4G4D1HBAIR(20M)@FBGA153 [DX5104-1]
THGBM4G4D1HBAIR(2G)@FBGA153 [DX5104-1]
THGBM4G5D1HBAIR(2G)@FBGA153 [DX5104]
THGBM4G8D4GBAIE(20M)@FBGA169 [DX5113-1]
THGBM4G8D4GBAIE(2G)@FBGA169 [DX5113-1]
THGBM4G9D8GBAII(20M)@FBGA169 [DX5170-1]
THGBM4G9D8GBAII(2G)@FBGA169 [DX5170-1]
THGBM5G5A1JBAIR(20M)@FBGA153 [DX5104-1]
THGBM5G5A1JBAIR(2G)@FBGA153 [DX5104-1]
THGBM5G6A2JBAIR(20M)@FBGA153 [DX5104-1]
THGBM5G6A2JBAIR(2G)@FBGA153 [DX5104-1]
THGBM5G7A2JBAIM(20M)@FBGA169 [DX5113-1]
THGBM5G7A2JBAIM(2G)@FBGA169 [DX5113-1]
THGBM5G7A2JBAIR(20M)@FBGA153 [DX5104-1]
THGBM5G7A2JBAIR(2G)@FBGA153 [DX5104-1]
THGBM5G8A4JBAIM(20M)@FBGA169 [DX5113-1]
THGBM5G8A4JBAIM(2G)@FBGA169 [DX5113-1]
TMM24128 [DX0001]
TMM24128A [DX0001]
TMM24128AP [DX0001]
TMM24256 [DX0001]
TMM24256A [DX0001]
TMM24256AP [DX0001]

TMM24256B [DX0001]
TMM24512 [DX0001]
TMM24512A [DX0001]
TMM24512P [DX0001]
TMM2464AP [DX0001]
TMM27128 [DX0001]
TMM27128A [DX0001]
TMM27128ADI [DX0001]
TMM27128AP [DX0001]
TMM27256 [DX0001]
TMM27256A [DX0001]
TMM27256AD [DX0001]
TMM27256ADI [DX0001]
TMM27256BD [DX0001]
TMM27256BDI [DX0001]
TMM27256D [DX0001]
TMM27256DI [DX0001]
TMM2732 [DX0001]
TMM2732A [DX0001]
TMM2732D [DX0001]
TMM27512 [DX0001]
TMM27512AD [DX0001]
TMM27512ADI [DX0001]
TMM27512D [DX0001]
TMM27512DI [DX0001]
TMM2764 [DX0001]
TMM2764AD [DX0001]
TMM2764ADI [DX0001]
TMM2764AP [DX0001]
TMM2764D [DX0001]
TMM2764DI [DX0001]
TV00560002ADBB@FBGA73 [DX5196]
TV00560002DDGB@FBGA81 [DX5196]
TV00560002EDGB@FBGA81 [DX5196]
TV00560003ADBB@FBGA73 [DX5196]
TV00560003EDGB@FBGA81 [DX5196]
TV00569002AABD(NOR)@FBGA107 [DX5084]
TV00569002BABD(NOR)@FBGA107 [DX5084]
TV00569003AABD(NOR)@FBGA107 [DX5084]
TV00569003BABD(NOR)@FBGA107 [DX5084]
TV00570002AABB@FBGA73 [DX5057]
TV00570002ADGB@FBGA85 [DX5196]
TV00570002CDGB@FBGA81 [DX5196]
TV00570003AABB@FBGA73 [DX5057]
TV00570003ADGB@FBGA85 [DX5196]
TV00570003CDGB@FBGA81 [DX5196]
TV00578002AABD(NOR)@FBGA107 [DX5084]
TV00578002CABD(NOR)@FBGA107 [DX5084]
TV00578003AABD(NOR)@FBGA107 [DX5084]
TV00578003CABD(NOR)@FBGA107 [DX5084]
TV00579002AABD(NOR)@FBGA107 [DX5084]
TV00579002AAGD(NOR)@FBGA107 [DX5084]
TV00579002EAGD(NOR)@FBGA107 [DX5084]
TV00579003AABD(NOR)@FBGA107 [DX5084]
TV00579003AAGD(NOR)@FBGA107 [DX5084]
TV00579003EAGD(NOR)@FBGA107 [DX5084]
TV0057A002AABD(NOR)@FBGA107 [DX5084]
TV0057A002CAGD(NOR)@FBGA107 [DX5084]
TV0057A002EAGD(NOR)@FBGA107 [DX5084]
TV0057A003AABD(NOR)@FBGA107 [DX5084]
TV0057A003CAGD(NOR)@FBGA107 [DX5084]
TV0057A003EAGD(NOR)@FBGA107 [DX5084]
TV00670002ADGB@FBGA81 [DX5196]
TV00670002CABB@FBGA73 [DX5196]
TV00670002CAGB@FBGA73 [DX5196]
TV00670002CDGB@FBGA81 [DX5196]
TV00670003ADGB@FBGA81 [DX5196]
TV00670003CABB@FBGA73 [DX5196]
TV00670003CAGB@FBGA73 [DX5196]
TV00670003CDGB@FBGA81 [DX5196]
TV0067A002AABD(NOR)@FBGA107 [DX5084]
TV0067A003AABD(NOR)@FBGA107 [DX5084]
TV0068A02SAAGD(NOR)@FBGA107 [DX5057]

TY00570002ARGQ@FBGA52 [DX5131]　　TY00570003ARGQ@FBGA52 [DX5131]
TY00670002ARGQ@FBGA52 [DX5131]　　TY00670003ARGQ@FBGA52 [DX5131]
TY00679002AAGD(NOR)@FBGA107 [DX5084]
TY00679003AAGD(NOR)@FBGA107 [DX5084]
TY00680002ADGB@FBGA81 [DX5196]　　TY00680002ARGQ@FBGA52 [DX5131]
TY00680003ADGB@FBGA81 [DX5196]　　TY00680003ARGQ@FBGA52 [DX5131]
TY5701111183KC04@FBGA52 [DX5131]　　TY6701111184KC04@FBGA52 [DX5131]
TY80009000ALKF@BGA149 [DX5013]　　TY80009000B6KU@FBGA130 [DX5140]
TY80009000FMGF@BGA149 [DX5013]　　TY80009000JMGF@BGA149 [DX5013]
TY8000A000ABKD40@FBGA107 [DX5084]
TY8000A000FMGF@FBGA149 [DX5013]　　TY8000A010AMGF@FBGA149 [DX5013]
TY8000A800AFGP10@FBGA137 [DX5011-1]
TY890A111122KA40@BGA130 [DX5155]
TY890A111222KA@FBGA130 [DX5140-1]
TY890A111229KC@FBGA149 [DX5013]　　TY890A111230KC@FBGA149 [DX5013]
TY890A111231KC@FBGA149 [DX5013]　　TY890A111288KA@FBGA130 [DX5140]
TY890A111359KA@FBGA130 [DX5140]
TY890A111411KA@FBGA130 [DX5140-1]
TY8A0A111111KC@BGA137 [DX5011]　　TY8A0A111151KC@BGA107 [DX5084]
TY8A0A111152KC@FBGA107 [DX5084]　　TY8A0A111161KC@FBGA107 [DX5084]
TY8A0A111170KC@TFBGA137 [DX5011]　　TY8A0A111173KC@TFBGA149 [DX5013]
TY8A0A111176LA@FBGA128 [DX5087]　　TY8A0A111180KA@FBGA130 [DX5140]
TY8A0A111291KA@FBGA130 [DX5140]　　TY8A0A111292KA@FBGA130 [DX5140]
TY8A0A111412KA@FBGA130 [DX5140]　　TY8A0A111414KC@FBGA137 [DX5011]
TY8A0A111434KA@FBGA130 [DX5140]　　TY8B0A111477KC@FBGA107 [DX5084]
TY90009000AMGF@FBGA149 [DX5013]　　TY90009000FMGF@FBGA149 [DX5013]
TY90009400DMGF@FBGA149 [DX5013]　　TY90009800A0GG@TFBGA225 [DX5017]
TY90009800C0GG@TFBGA225 [DX5017]　　TY9000A000ABKD@BGA107 [DX5084]
TY9000A000AMGF@BGA149 [DX5013]　　TY9000A000EMGF@BGA149 [DX5013]
TY9000A000FLKF@BGA149 [DX5013]　　TY9000A000GMGF@BGA149 [DX5013]
TY9000A000MMGF@BGA149 [DX5013]　　TY9000A400AMGF@BGA149 [DX5013]
TY9000A80000GG@TFBGA225 [DX5017]　　TY9000A800D0GG@TFBGA225 [DX5017]
TY9000A800E0GG@TFBGA225 [DX5017]　　TY9000A800G0GG@TFBGA225 [DX5017]
TY9000A800H0GG@BGA225 [DX5017]　　TY9000A800K0GG@FBGA225 [DX5017]
TY9000A800K0GG40@BGA225 [DX5017]　　TY9000A800M0GG@TFBGA225 [DX5017]
TY9A0A111103GC@TFBGA137 [DX5011]　　TY9A0A111110KC@FBGA149 [DX5013]
TY9A0A111171KC@BGA107 [DX5084]　　TY9A0A111174KC@BGA149 [DX5013]
TY9A0A111189KC@BGA149 [DX5013]　　TY9A0A111208KA@FBGA130 [DX5140]
TY9A0A111283KA@FBGA107 [DX5084]　　TY9A0A111295KA@FBGA130 [DX5140]
TY9A0A111296KC@FBGA130 [DX5155]　　TY9A0A111297KC@FBGA107 [DX5084]
TY9A0A111300KA@FBGA130 [DX5140-1]
TY9A0A111308LA@FBGA130 [DX5140-1]
TY9A0A111527KA@FBGA130 [DX5140]　　TYA000B000ALKF@BGA149 [DX5013]
TYA000B000BLKF@BGA149 [DX5013]　　TYA000B400ALHF@FBGA149 [DX5013]
TYA000B800C0GG@FBGA225 [DX5017]　　TYA000BC00J0GG@TFBGA225 [DX5017]
TYA000BC10A0GG@TFBGA225 [DX5017]　　TYA000BC10D0GG@TFBGA225 [DX5017]
TYA000BC10H0GG@TFBGA225 [DX5017]　　TYAB0A111072KC@FBGA130 [DX5155]
TYAB0A111081KC@FBGA225 [DX5017]　　TYAB0A111128KC@FBGA107 [DX5084]

TYAB0A111254KA@FBGA130 [DX5140]
TYAB0A111255KA20@FBGA130 [DX5140]
TYAB0A111463KA@FBGA130 [DX5140]
TYAB0A111480KA@FBGA130 [DX5140]
TYBC0A111086KC@FBGA137 [DX5011]
TYBC0A111118L9@BGA152 [DX5254]
TYBC0A111430KC@FBGA137 [DX5011]
TYBC0A211337KC@FBGA130 [DX5155]
TYBD0A121356LC@FBGA137 [DX5011]
TYCC0A211120KC40@FBGA137 [DX5011]

DRAM & SRAM

TC518128 [DX0001]
TC518128@SOIC32 [DX1035]
TC518129 [DX0001]
TC518129@SOIC32 [DX1035]
TC51832
TC51832@SOIC28 [DX1035]
TC518512 [DX0001]
TC518512@SOIC32 [DX1035]
TC551001FL [DX0001]
TC551001FL@SOIC32 [DX1035]
TC551001PL [DX0001]
TC551001PL@SOIC32 [DX1035]
TC55257 [DX0001]
TC55257@SOIC28 [DX1035]
TC55257L [DX0001]
TC55257L@SOIC28 [DX1035]
TC55258 [DX0001]
TC55258@SOIC28 [DX1035]
TC55258L [DX0001]
TC55258L@SOIC28 [DX1035]
TC55328 [DX0001]
TC55328@SOIC28 [DX1035]
TC5563APL [DX0001]
TC5563APL@SOIC28 [DX1035]
TC5564APL [DX0001]
TC5564APL@SOIC28 [DX1035]
TC5565AFL [DX0001]
TC5565AFL@SOIC28 [DX1035]
TC5565APL [DX0001]
TC5565APL@SOIC28 [DX1035]
TC5588 [DX0001]
TC5588@SOIC28 [DX1035]
TC55B88 [DX0001]
TC55B88@SOIC28 [DX1035]
TMM2063 [DX0001]
TMM2063@SOIC28 [DX1035]

MICROCONTROLLER

TMP47P201VP
TMP47P202VM@SOIC20 [DX1021]
TMP47P202VP
TMP47P206VM@SOIC20 [DX1021]
TMP47P206VP
TMP47P241VM@SOIC28 [DX1035]
TMP47P241VMG@SOIC28 [DX1035]
TMP47P241VN@SDIP28 [DX0032]
TMP47P241VNG@SDIP28 [DX0032]
TMP47P403VM@SOIC28 [DX1033]
TMP47P403VMG@SOIC28 [DX1033]
TMP47P403VN@SDIP28 [DX0032]
TMP47P403VNG@SDIP28 [DX0032]
TMP47P422VF@QFP44 [DX3004]
TMP47P422VFG@QFP44 [DX3004]
TMP47P422VN@SDIP42 [DX0042]
TMP47P422VNG@SDIP42 [DX0042]
TMP47P422VU@QFP44 [DX3005]
TMP47P422VUG@QFP44 [DX3005]
TMP47P440VF@QFN44 [DX3004]
TMP47P440VFG@QFN44 [DX3004]
TMP47P440VN@SDIP42 [DX0042]
TMP47P440VNG@SDIP42 [DX0042]
TMP47P443VM@SOIC28 [DX1033]
TMP47P443VMG@SOIC28 [DX1033]
TMP47P443VN@SDIP28 [DX0032]
TMP47P443VNG@SDIP28 [DX0032]
TMP68HC11A0 [DX0001]
TMP68HC11A0@PLCC52 [DX2052]
TMP68HC11A1 [DX0001]

TMP68HC11A1@PLCC52 [DX2052]
TMP68HC11A8 [DX0001]
TMP68HC11A8@PLCC52 [DX2052]
TMP68HC11E1@PLCC52 [DX2052]
TMP68HC11E1@QFP52 [DX3010]
TMP68HC11E9@PLCC52 [DX2052]
TMP68HC11E9@QFP52 [DX3010]
TMP68HC711E9@PLCC52 [DX2052]
TMP68HCP11A0 [DX0001]
TMP68HCP11A0@PLCC52 [DX2052]
TMP68HCP11A1 [DX0001]
TMP68HCP11A1@PLCC52 [DX2052]
TMP68HCP11A8 [DX0001]
TMP68HCP11A8@PLCC52 [DX2052]
TMP86F809NG@SDIP32 [DX0032]
TMP86FH09AMG [DX1069]
TMP86FH09ANG@SDIP32 [DX0032]
TMP86FH09BMG [DX1069]
TMP86FH09BNG [DX0032]
TMP86FH409NG@SDIP32 [DX0032]
TMP86FH46ANG@SDIP42 [DX0042]
TMP86FH46BNG@SDIP42 [DX0042]
TMP86FH47ADUG@QFP48 [DX3007]
TMP86FH47AUG@QFP44 [DX3005]
TMP86FH47BUG@QFP44 [DX3005]
TMP86FH92DMG@SSOP30 [DX1026]
TMP86FH92IDMG@SSOP30 [DX1026]
TMP86FS49AFG@QFP64 [DX3014]
TMP86FS49AIFG@QFP64 [DX3014]
TMP86FS49AIUG@QFP64 [DX3011]
TMP86FS49AUG@QFP64 [DX3011]
TMP86FS49BFG@QFP64 [DX3014]
TMP86FS49BUG@QFP64 [DX3011]
TMP86P202M@SOIC20 [DX1031]
TMP86P202P
TMP86P203M@SOIC20 [DX1031]
TMP86P203P
TMP86P807M@SOP28 [DX1019]
TMP86P807MG@SOP28 [DX1019]
TMP86P807N@SDIP28 [DX0032]
TMP86P807NG@SDIP28 [DX0032]
TMP86P808DM@SSOP30 [DX1026]
TMP86P808DMG@SSOP30 [DX1026]
TMP86P808N@SDIP30 [DX0032]
TMP86P808NG@SDIP30 [DX0032]
TMP86PH06N@SDIP42 [DX0042]
TMP86PH06NG@SDIP42 [DX0042]
TMP86PH06U@QFP44 [DX3005]
TMP86PH06UG@QFP44 [DX3005]
TMP86PH46N@SDIP42 [DX0042]
TMP86PH46NG@SDIP42 [DX0042]
TMP86PH47U@QFP44 [DX3005]
TMP86PH47UG@QFP44 [DX3005]
TMP86PM29AF@QFP64 [DX3014]
TMP86PM29AU@QFP64 [DX3011]
TMP86PM46N@SDIP42 [DX0042]
TMP86PM46NG@SDIP42 [DX0042]
TMP86PM47AU@QFP44 [DX3005]
TMP86PM47AUG@QFP44 [DX3005]
TMP86PM47U@QFP44 [DX3005]
TMP86PM47UG@QFP44 [DX3005]
TMP86PM72F@QFP64 [DX3014]
TMP86PM72FG@QFP64 [DX3014]
TMP86PM74AF@PQFP80 [DX3019]
TMP86PM74AFG@PQFP80 [DX3019]
TMP86PM74F@PQFP80 [DX3019]
TMP86PM74FG@PQFP80 [DX3019]
TMP86PS44U@QFP44 [DX3005]
TMP86PS44UG@QFP44 [DX3005]
TMP87P408M@SOIC28 [DX1035]
TMP87P408N@SDIP28 [DX0032]
TMP87P409M@SOIC28 [DX1035]
TMP87P409N@SDIP28 [DX0032]
TMP87P808LM@SOP28 [DX1035]
TMP87P808LN@SDIP28 [DX0032]
TMP87P808M@SOP28 [DX1035]
TMP87P808N@SDIP28 [DX0032]
TMP87P809M@SOIC28 [DX1035]
TMP87P809N@SDIP28 [DX0032]
TMP87P844N@SDIP42 [DX0042]
TMP87P844NG@SDIP42 [DX0042]
TMP87PH00DF@QFP64 [DX3014]
TMP87PH00DFG@QFP64 [DX3014]
TMP87PH00F@QFP64 [DX3015]
TMP87PH00FG@QFP64 [DX3015]
TMP87PH00LF@QFP64 [DX3014]
TMP87PH00LFG@QFP64 [DX3014]
TMP87PH00N@SDIP64 [DX0064]
TMP87PH00NG@SDIP64 [DX0064]
TMP87PH20F@QFP80 [DX3019]
TMP87PH20FG@QFP80 [DX3019]
TMP87PH40AF@PQFP64 [DX3015]
TMP87PH40AFG@PQFP64 [DX3015]
TMP87PH40AN@SDIP64 [DX0064]
TMP87PH40ANG@SDIP64 [DX0064]
TMP87PH46N@SDIP42 [DX0042]

TMP87PH46NG@SDIP42 [DX0042]
TMP87PH47LUG@QFP44 [DX3005]
TMP87PH47UG@QFP44 [DX3005]
TMP87PH48DFG@LQFP64 [DX3014]
TMP87PH48UG@LQFP64 [DX3011]
TMP87PM14FG@QFP64 [DX3015]
TMP87PM14NG@SDIP64 [DX0064]
TMP87PM20FG@QFP80 [DX3019]
TMP87PM29NG@SDIP64 [DX0064]
TMP87PM29UG@LQFP64 [DX3011]
TMP87PM40AFG@PQFP64 [DX3015]
TMP87PM40ANG@SDIP64 [DX0064]
TMP87PM41FG@QFP64 [DX3015]
TMP87PM41NG@SDIP64 [DX0064]
TMP87PM41UG@LQFP64 [DX3011]
TMP87PM43NG@SDIP42 [DX0042]
TMP87PM48DFG@LQFP64 [DX3014]
TMP87PM48UG@LQFP64 [DX3011]
TMP87PM53FG@PQFP80 [DX3019]
TMP87PM70FG@QFP80 [DX3019]
TMP87PM74FG@QFP80 [DX3019]
TMP87PM75FG@QFP100 [DX3023]
TMP87PM78FG@QFP100 [DX3023]
TMP87PP21DFG@QFP80 [DX3016]
TMP87PP21FG@QFP80 [DX3016]
TMP87PP23FG@PQFP100 [DX3023]
TMP87PP24AFG@QFP100 [DX3021]
TMP87PP24FG@QFP100 [DX3021]
TMP87PP71FG@PQFP80 [DX3019]
TMP87PS64FG@PQFP100 [DX3023]
TMP87PS68FG@QFP80 [DX3016]
TMP87PS71AFG@PQFP80 [DX3019]
TMP87PS71FG@PQFP80 [DX3019]
TMP88FW45AFG@PQFP80 [DX3019]
TMP88PH40M@SOIC28 [DX1064]
TMP88PH40N@SDIP28 [DX0032]
TMP88PS42F@PQFP64 [DX3015]
TMP88PS42N@SDIP64 [DX0064]
TMP89FH42AUG@QFP44 [DX3003]
TMP89FM42AUG@QFP44 [DX3003]
TMP89FM82DUG@QFP48 [DX3007]
TMP91FU62DFG@PQFP80 [DX3019]
TMP91PW10F@QFP100 [DX3021]
TMP91PW11F@QFP100 [DX3021]
TMP91PW12F@QFP100 [DX3021]
TMP91PW18AF@PQFP80 [DX3019]
TMP93PS40DF@QFP100 [DX3021]
TMP93PS40F@QFP100 [DX3021]
TMP87PH47LU@QFP44 [DX3005]
TMP87PH47U@QFP44 [DX3005]
TMP87PH48DF@LQFP64 [DX3014]
TMP87PH48U@LQFP64 [DX3011]
TMP87PM14F@QFP64 [DX3015]
TMP87PM14N@SDIP64 [DX0064]
TMP87PM20F@QFP80 [DX3019]
TMP87PM29N@SDIP64 [DX0064]
TMP87PM29U@LQFP64 [DX3011]
TMP87PM40AF@PQFP64 [DX3015]
TMP87PM40AN@SDIP64 [DX0064]
TMP87PM41F@QFP64 [DX3015]
TMP87PM41N@SDIP64 [DX0064]
TMP87PM41U@LQFP64 [DX3011]
TMP87PM43N@SDIP42 [DX0042]
TMP87PM48DF@LQFP64 [DX3014]
TMP87PM48U@LQFP64 [DX3011]
TMP87PM53F@PQFP80 [DX3019]
TMP87PM70F@QFP80 [DX3019]
TMP87PM74F@QFP80 [DX3019]
TMP87PM75F@QFP100 [DX3023]
TMP87PM78F@QFP100 [DX3023]
TMP87PP21DF@QFP80 [DX3016]
TMP87PP21F@PQFP80 [DX3019]
TMP87PP23F@PQFP100 [DX3023]
TMP87PP24AF@QFP100 [DX3021]
TMP87PP24F@QFP100 [DX3021]
TMP87PP71F@PQFP80 [DX3019]
TMP87PS64F@PQFP100 [DX3023]
TMP87PS68F@QFP80 [DX3016]
TMP87PS71AF@PQFP80 [DX3019]
TMP87PS71F@PQFP80 [DX3019]
TMP88FH41UG@QFP44 [DX3005]
TMP88FW45FG@PQFP80 [DX3019]
TMP88PH40MG@SOIC28 [DX1064]
TMP88PH40NG@SDIP28 [DX0032]
TMP88PS42FG@PQFP64 [DX3015]
TMP88PS42NG@SDIP64 [DX0064]
TMP89FH42UG@QFP44 [DX3003]
TMP89FM42UG@QFP44 [DX3003]
TMP89FS60FG [DX3014]
TMP91FU62FG@QFP80 [DX3016]
TMP91PW10FG@QFP100 [DX3021]
TMP91PW11FG@QFP100 [DX3021]
TMP91PW12FG@QFP100 [DX3021]
TMP91PW18AFG@PQFP80 [DX3019]
TMP93PS40DFG@QFP100 [DX3021]
TMP93PS40FG@QFP100 [DX3021]

TMP93PS44F@QFP80 [DX3016]
TMP93PS44FG@QFP80 [DX3016]
TMP93PW20AF@QFP144 [DX3034]
TMP93PW20AFG@QFP144 [DX3034]
TMP93PW32F@QFP64 [DX3014]
TMP93PW32FG@QFP64 [DX3014]
TMP93PW40DF@QFP100 [DX3021]
TMP93PW40DFG@QFP100 [DX3021]
TMP93PW44ADF@PQFP80 [DX3019]
TMP93PW44ADFG@PQFP80 [DX3019]
TMP93PW46AF@QFP100 [DX3021]
TMP93PW46AFG@QFP100 [DX3021]
TMP95PW64F@QFP100 [DX3021]
TMP95PW64FG@QFP100 [DX3021]
TMP96PM40F@PQFP80 [DX3019]
TMP96PM40FG@PQFP80 [DX3019]
TMPM342@FBGA142 [DX5251]
TMPM370FYAFG@QFP100 [DX3021]
TMPM370FYDFG@QFP100 [DX3077]
TMPM370FYFG@QFP100 [DX3021]
TMPM374FWUG@QFP44 [DX3005]
TMPM375(UART)@TSSOP30 [DX1087]
TMPM376FDFG@QFP100 [DX3021]
TMPM376FYFG@QFP100 [DX3021]

TOSHIBA-CUSTOMER

E(E)PROM/FRAM/NVRAM

TC58NVG0S3CTA00(DAYAN)@TSOP48 [DX1004]
TC58NVG0S3EBAI4(CHUANGJ)@FBGA63 [DX5046]
TC58NVG0S3EBAI4(JiuZhou)@FBGA63 [DX5046]
TC58NVG0S3ETA00(DAYAN)@TSOP48 [DX1004-1]
TC58NVG0S3ETA00(New)@TSOP48 [DX1004-3]
TC58NVG0S3ETA00(REALTEK)@TSOP48 [DX1004-1]
TC58NVG0S3ETA00(ST7162)@TSOP48 [DX1004]
TC58NVG0S3ETA00@TSOP48(DaXian) [DX1004-1]
TC58NVG0S3HBAI4(ST273)@FBGA63 [DX5046-1]
TC58NVG0S3HTA00(ST273)@TSOP48 [DX1004-3]
TC58NVG1S3ETA00(MSTAR)@TSOP48 [DX1004-1]
TC58NVG1S3ETA00(PICOCHIP)@TSOP48 [DX1004-1]
TC58NVG1S3ETA00(ST7142)@TSOP48 [DX1004]
TC58NVG1S3HTA00(ST273)@TSOP48 [DX1004-3]
TC58NVG3S0FTA00(slow)@TSOP48 [DX1004-1]
TC58NYG1S3EBAI5(slow)@FBGA63 [DX5168]
TH58NVG5S0FTAK0(LINKS)@TSOP48 [DX1004-1]
TH58NVG6S2FTA20(Viking)@TSOP48 [DX1004-1]
TH58NVG7S2FTA30(Viking)@TSOP48 [DX1004-1]
THGBM2G6D2FBAI9(INTEL)(20M) [DX5158]
THGBM2G6D2FBAI9(INTEL)(2G) [DX5158]
THGBM2G7D4FBAI9(INTEL)(20M) [DX5158]
THGBM2G7D4FBAI9(INTEL)(2G) [DX5158]
THGBM2G8D8FBAI2(INTEL)(20M) [DX5158]
THGBM2G8D8FBAI2(INTEL)(2G) [DX5158]
THGBM2G8D8FBAIB(INTEL)(20M) [DX5158]
THGBM2G8D8FBAIB(INTEL)(2G) [DX5158]
THGBM2G8D8FBAIB(INTEL)(32G) [DX5158]
THGBM4G4D1HBAIR(HAIER)@FBGA153 [DX5104-1]
THGBM5G8A4JBAIM(INTEL)(20M) [DX5158]

THGBM5G8A4JBAIM(INTEL)(2G) [DX5158]
TY8A0A111161KC(XSR)@BGA107 [DX5084]
TY8A0A111290KA(XSR1.0)@BGA130 [DX5140]
TY8A0A111291KA(ICERA)@FBGA130 [DX5140]
TY8A0A111434KA(ICERA)@FBGA130 [DX5140]
TY8A0A111487KA(ICERA)@FBGA130 [DX5140]
TY9A0A111296KC(XSR1.0)@FBGA130 [DX5155]
TY9A0A111300KA(INVENTEC)@FBGA130 [DX5140]
TYAB0A111072KC(BROADCOM)@FBGA130 [DX5155]
TYBC0A211337KC(BCM-IAC)@FBGA130 [DX5155]
TYBC0A211337KC(BROADCOM)@FBGA130 [DX5155]

TURBO IC

E(E)PROM/FRAM/NVRAM

TU24C01 [DX0001]
TU24C02 [DX0001]
TU24C04 [DX0001]
TU24C08 [DX0001]
TU24C128 [DX0001]
TU24C16 [DX0001]
TU24C16@TSSOP8 [DX1059]
TU24C256@SOIC8 [DX1045]
TU24C32@SOIC8 [DX1045]
TU24C64@SOIC8 [DX1045]
TU24C01@SOIC8 [DX1045]
TU24C02@SOIC8 [DX1045]
TU24C04@SOIC8 [DX1045]
TU24C08@SOIC8 [DX1045]
TU24C128@SOIC8 [DX1045]
TU24C16@SOIC8 [DX1045]
TU24C256 [DX0001]
TU24C32 [DX0001]
TU24C64 [DX0001]

UBICOM

MICROCONTROLLER

SX20AC/SS/G@SSOP20 [DX1026]
SX28AC/DP [DX0001]
SX28AC/SS/G@SSOP28 [DX1026]
SX48BD/G@TQFP48 [DX3047]
SX20AC/SS@SSOP20 [DX1026]
SX28AC/DP/G [DX0001]
SX28AC/SS@SSOP28 [DX1026]
SX48BD@TQFP48 [DX3047]

UMC

E(E)PROM/FRAM/NVRAM

2732 [DX0001]
2764 [DX0001]

DRAM & SRAM

UM61256 [DX0001]
UM61256@SOIC28 [DX1035]

UM61512 [DX0001]
UM61512@SOIC32 [DX1035]
UM6164 [DX0001]
UM6164@SOIC28 [DX1035]
UM621024 [DX0001]
UM621024@SOIC32
UM62256 [DX0001]
UM62256@SOIC28 [DX1035]
UM62256A [DX0001]
UM62256A@SOIC28 [DX1035]
UM6264 [DX0001]
UM6264@SOIC28 [DX1035]
UM6264A [DX0001]
UM6264A@SOIC28 [DX1035]

UNIGEN

E(E)PROM/FRAM/NVRAM

UG24C01 [DX0001]
UG24C01@SOP8 [DX1045]
UG24C01@TSSOP8 [DX1059]
UG24C02 [DX0001]
UG24C02@SOP8 [DX1045]
UG24C02@TSSOP8 [DX1059]
UG24C04 [DX0001]
UG24C04@SOP8 [DX1045]
UG24C04@TSSOP8 [DX1059]
UG24C08 [DX0001]
UG24C08@SOP8 [DX1045]
UG24C08@TSSOP8 [DX1059]
UG24C16 [DX0001]
UG24C16@SOP8 [DX1045]
UG24C16@TSSOP8 [DX1059]

VANTIS

PLD

iM4A3-192/96@VQFP144 [DX3035]
iM4A5-192/96@VQFP144 [DX3035]
M4-128/64@PQFP100 [DX3022]
M4-128/64@TQFP100 [DX3021]
M4-128N/64@PLCC84 [DX2084]
M4-192/96@VQFP144 [DX3035]
M4-32/32@PLCC44 [DX2044]
M4-32/32@TQFP44 [DX3003]
M4-32/32@TQFP48 [DX3007]
M4-64/32@PLCC44 [DX2044]
M4-64/32@TQFP44 [DX3003]
M4-64/32@TQFP48 [DX3007]
M4-96/48@TQFP100 [DX3021]
M4A3-128/64@PQFP100 [DX3022]
M4A3-128/64@TQFP100 [DX3021]
M4A3-128N/64@PLCC84 [DX2084]
M4A3-32/32@PLCC44 [DX2044]
M4A3-32/32@TQFP44 [DX3003]
M4A3-32/32@TQFP48 [DX3007]
M4A3-384-160 [DX3118]
M4A3-384-192 [DX0001]
M4A3-512-160 [DX3118]
M4A3-512-192 [DX0001]
M4A3-512-256 [DX0001]
M4A3-64/32@PLCC44 [DX2044]
M4A3-64/32@TQFP44 [DX3003]
M4A3-64/32@TQFP48 [DX3007]
M4A3-64/64@TQFP100 [DX3021]
M4A3-96/48@TQFP100 [DX3021]
M4A5-128/64@PQFP100 [DX3022]
M4A5-128/64@TQFP100 [DX3021]
M4A5-128N/64@PLCC84 [DX2084]
M4A5-32/32@PLCC44 [DX2044]
M4A5-32/32@TQFP44 [DX3003]
M4A5-32/32@TQFP48 [DX3007]
M4A5-64/32@PLCC44 [DX2044]
M4A5-64/32@TQFP44 [DX3003]
M4A5-64/32@TQFP48 [DX3007]
M4A5-96/48@TQFP100 [DX3021]
M4LV-128/64@PQFP100 [DX3022]
M4LV-128/64@TQFP100 [DX3021]
M4LV-128N/64@PLCC84 [DX2084]

M4LV-32/32@PLCC44 [DX2044]
M4LV-32/32@TQFP44 [DX3003]
M4LV-32/32@TQFP48 [DX3007]
M4LV-64/32@PLCC44 [DX2044]
M4LV-64/32@TQFP44 [DX3003]
M4LV-64/32@TQFP48 [DX3007]
M4LV-96/48@TQFP100 [DX3021]
MACH110@PLCC44 [DX2044]
MACH111@PLCC44 [DX2044]
MACH111@TQFP44 [DX3003]
MACH120@PLCC68 [DX2068]
MACH130@PLCC84 [DX2084]
MACH131/1@PLCC84 [DX2084]
MACH131@PLCC84 [DX2084]
MACH131SP@PQFP100 [DX3022]
MACH131SP@TQFP100 [DX3021]
MACH210@PLCC44 [DX2044]
MACH210@TQFP44 [DX3003]
MACH210A@PLCC44 [DX2044]
MACH210A@TQFP44 [DX3003]
MACH210AQ@PLCC44 [DX2044]
MACH210AQ@TQFP44 [DX3003]
MACH211@PLCC44 [DX2044]
MACH220@PLCC68 [DX2068]
MACH221@PLCC68 [DX2068]
MACH231SP@PLCC84 [DX2084]
MACH231SP@PQFP100 [DX3022]
MACH231SP@TQFP100 [DX3021]
MACH435@PLCC84 [DX2084]
MACH436@PLCC84 [DX2084]
MACH446@PQFP100 [DX3022]
MACH446@TQFP100 [DX3021]
MACHLV210@PLCC44 [DX2044]
MACHLV210@TQFP44 [DX3003]
MACHLV436@PLCC84 [DX2084]
MACHLV446@PQFP100 [DX3022]
MACHLV446@TQFP100 [DX3021]
PAL29M16H [DX0001]
PALCE20RA10 [DX0001]
PALCE20RA10@PLCC28 [DX2028]
PALCE20RA10@SOIC24 [DX1033]
PALCE20RA10H [DX0001]
PALCE20RA10H@PLCC28 [DX2028]
PALCE20RA10H@SOIC24 [DX1033]
PALCE20RA10Q [DX0001]
PALCE20RA10Q@PLCC28 [DX2028]
PALCE20RA10Q@SOIC24 [DX1033]
PALCE26V12H/4 [DX0001]
PALCE26V12H/4@PLCC28 [DX2028]
PALCE26V12H/4@SOIC28 [DX1033]
PALCE26V12H-15 [DX0001]
PALCE26V12H-15@PLCC28 [DX2028]
PALCE26V12H-15@SOIC28 [DX1033]
PALCE26V12H-20 [DX0001]
PALCE26V12H-20@PLCC28 [DX2028]
PALCE26V12H-20@SOIC28 [DX1033]
PALCE26V12H-25 [DX0001]
PALCE26V12H-25@PLCC28 [DX2028]
PALCE26V12H-25@SOIC28 [DX1033]
PALCE29M16H [DX0001]
PALCE29M16H@PLCC28 [DX2028]
PALCE29M16H@SOIC24 [DX1033]
PALCE29MA16H [DX0001]
PALCE29MA16H@PLCC28 [DX2028]
PALCE29MA16H@SOIC24 [DX1033]
PALCE610 [DX0001]
PALCE610@PLCC28 [DX2028]
PALCE610@SOIC24 [DX1003]
PALCE610H [DX0001]
PALCE610H@PLCC28 [DX2028]
PALCE610H@SOIC24 [DX1003]
PALCE630H [DX0001]
PALCE630H@PLCC28 [DX2028]
PALCE630H@SOIC24 [DX1003]

VERSACHIPS

MICROCONTROLLER

V87C54 [DX0001]
V87C54@PLCC44 [DX2044]
V87C54@TQFP44 [DX3003]
V87C58 [DX0001]
V87C58@PLCC44 [DX2044]
V87C58@TQFP44 [DX3003]

VLSI

E(E)PROM/FRAM/NVRAM

VT27C128 [DX0001]
VT27C256 [DX0001]
VT27C512 [DX0001]
VT27C64 [DX0001]
VT28H64 [DX0001]
VT28HC64 [DX0001]

PLD

GAL16V8 [DX0001]

WELTREND

MICROCONTROLLER

WT61P4K420@SDIP42 [DX0042]
WT61P4K421@SDIP42 [DX0042]
WT61P4K422@SDIP42 [DX0042]
WT61P4L440@PLCC44 [DX2044]
WT61P4N400 [DX0001]
WT61P4N401 [DX0001]
WT61P6K420@SDIP42 [DX0042]
WT61P6L440@PLCC44 [DX2044]
WT61P6L441@PLCC44 [DX2044]
WT61P6S@TQFP44 [DX3003]
WT61P7@LQFP44 [DX3003]
WT61P7@PLCC44 [DX2044]
WT61P7@TQFP48 [DX3007]
WT61P8@TQFP44 [DX3003]
WT61P8S@TQFP44 [DX3003]
WT62P1-K42@SDIP42 [DX0042]
WT62P1-N28(dip28) [DX0001]
WT62P1-N40(dip40) [DX0001]
WT62P1-N42(dip42) [DX0001]
WT62P1-S44@PSOP44 [DX1014]
WT62P2-K42@SDIP42 [DX0042]
WT62P2-L44@PLCC44 [DX2044]
WT62P2-N40(dip40) [DX0001]
WT62P2-N42(dip42) [DX0001]
WT62P2-S44@PSOP44 [DX1014]
WT6702F@SOP16 [DX1016]
WT6702F@SOP20 [DX1033]
WT6702F@SOP24 [DX1033]
WT6702F@SSOP20 [DX1025]
WT6703F@SOP20 [DX1033]
WT6703F@SOP24 [DX1033]
WT6703F@SOP28 [DX1033]
WT6703F@SSOP20 [DX1025]
WT6703F@SSOP24 [DX1025]
WT6703FS161@SSOP16 [DX1016]
WT6703FS163@SSOP16 [DX1016]

WHITE ELECTRONIC DESIGNS

E(E)PROM/FRAM/NVRAM

WE128K8 [DX0001]
WE256K8 [DX0001]
WE512K8 [DX0001]
WF256K8 [DX0001]
WF256K8@CLCC32 [DX2032]
WF256K8@CSOJ32 [DX1038]
WF2M32-90HM5@PGA66 [DX5000]
WF2M32-XG2UX5@CQFP68 [DX2168]
WF512K32N-XH1X5@PGA66 [DX5000]
WF512K32-XG2UX5@CQFP68 [DX2168]
WF512K8 [DX0001]
WF512K8@CLCC32 [DX2032]
WF512K8@CSOJ32 [DX1038]
WME128K8 [DX0001]

WME128K8@CLCC32 [DX2032]
WME128K8@CSOJ32 [DX1038]
WMF128K8 [DX0001]
WMF128K8@CLCC32 [DX2032]
WMF128K8@CSOJ32 [DX1038]
WMF256K8 [DX0001]
WMF256K8@CLCC32 [DX2032]
WMF256K8@CSOJ32 [DX1038]
WMF512K8 [DX0001]
WMF512K8@CLCC32 [DX2032]
WMF512K8@CSOJ32 [DX1038]
WMS128K8 [DX0001]
WMS128K8@CLCC32 [DX2032]
WMS128K8@CSOJ32 [DX1038]
WMS256K8 [DX0001]
WMS256K8@CLCC32 [DX2032]
WMS256K8@CSOJ32 [DX1038]
WMS512K8 [DX0001]
WMS512K8@CLCC32 [DX2032]
WMS512K8@CSOJ32 [DX1038]
WSF128K16@PGA66 [DX5000]

WINBOND

E(E)PROM/FRAM/NVRAM

W19B160BBB@FBGA48 [DX5002]
W19B160BBT@TSOP48 [DX1004]
W19B160BTB@FBGA48 [DX5002]
W19B160BTT@TSOP48 [DX1004]
W19B320ABB@FBGA48 [DX5001]
W19B320ABT@TSOP48 [DX1004]
W19B320ATB@FBGA48 [DX5001]
W19B320ATT@TSOP48 [DX1004]
W19B320BBB@FBGA48 [DX5001]
W19B320BBT@TSOP48 [DX1004]
W19B320BTB@FBGA48 [DX5001]
W19B320BTT@TSOP48 [DX1004]
W19B320SBB@FBGA48 [DX5001]
W19B320SBT@TSOP48 [DX1004]
W19B320STB@FBGA48 [DX5001]
W19B320STT@TSOP48 [DX1004]
W19B322MBB@FBGA48 [DX5001]
W19B322MBT@TSOP48 [DX1004]
W19B322MTB@FBGA48 [DX5001]
W19B322MTT@TSOP48 [DX1004]
W19B323MBB@FBGA48 [DX5001]
W19B323MBT@TSOP48 [DX1004]
W19B323MTB@FBGA48 [DX5001]
W19B323MTT@TSOP48 [DX1004]
W19B324MBB@FBGA48 [DX5001]
W19B324MBT@TSOP48 [DX1004]
W19B324MTB@FBGA48 [DX5001]
W19B324MTT@TSOP48 [DX1004]
W19L320SBB@FBGA48 [DX5001]
W19L320SBT@TSOP48 [DX1004]
W19L320STB@FBGA48 [DX5001]
W19L320STT@TSOP48 [DX1004]
W25B40(Bottom Boot)@MLP8 [DX4005#1]
W25B40(Bottom Boot)@SOIC8 [DX1045#1]
W25B40(Top Boot)@MLP8 [DX4005#1]
W25B40(Top Boot)@SOIC8 [DX1045#1]
W25B40A(Bottom Boot)@MLP8 [DX4005#1]
W25B40A(Bottom Boot)@SOIC8 [DX1045#1]
W25B40A(Top Boot)@MLP8 [DX4005#1]
W25B40A(Top Boot)@SOIC8 [DX1045#1]
W25D10 [DX0001]
W25D10(SN)@SOIC8 [DX1045]
W25D10(SS)@SOIC8 [DX1044]
W25D10(ZP)@WSON8 [DX4005]
W25D16@SOIC16 [DX1072#1]
W25D16@SOIC8 [DX1044#1]
W25D20 [DX0001]
W25D20(SN)@SOIC8 [DX1045]
W25D20(SS)@SOIC8 [DX1044]
W25D20(ZP)@WSON8 [DX4005]
W25D40 [DX0001]
W25D40(SN)@SOIC8 [DX1045]
W25D40(SS)@SOIC8 [DX1044]
W25D40(ZP)@WSON8 [DX4005]

W25D80 [DX0001]
W25D80(SS)@SOIC8 [DX1044]
W25N01GVZEIG@WSON8 [DX4006]
W25P10@MLP8 [DX4005]
W25P16@MLP8 [DX4005#1]
W25P16@SOIC16 [DX1072#1]
W25P16@SOIC8 [DX1044#1]
W25P20@MLP8 [DX4005#1]
W25P32@MLP8 [DX4005#1]
W25P32@SOIC16 [DX1072#1]
W25P40@MLP8 [DX4005#1]
W25P64@MLP8 [DX4005#1]
W25P64@SOIC16 [DX1072#1]
W25P80@MLP8 [DX4005#1]
W25Q05CV-SD8 [DX1059]
W25Q05CV-UX8 [DX4047]
W25Q10CV-SD8 [DX1059]
W25Q10CV-UX8 [DX4047]
W25Q128BV@SOIC16 [DX1033#1]
W25Q128FV [DX0001#1]
W25Q128FV@SOIC8 [DX1044#1]
W25Q128FV@TFBGA24[5*5] [DX5157]
W25Q128FV@VSOP8 [DX1044#1]
W25Q128FW [DX0001#1]
W25Q128FW@SOIC8 [DX1044#1]
W25Q128FW@TFBGA24[5*5] [DX5157]
W25Q128FW@VSOP8 [DX1044#1]
W25Q16@MLP8 [DX4005#1]
W25Q16@SOIC16 [DX1072#1]
W25Q16@SOIC8 [DX1044#1]
W25Q16BV [DX0001#1]
W25Q16BV(SN)@SOIC8 [DX1045#1]
W25Q16BV(ZP)@WSON8 [DX4005#1]
W25Q16CL(SF)@SOIC16 [DX1033#1]
W25Q16CL(SS)@SOIC8 [DX1044#1]
W25Q16CV(SF)@SOIC16 [DX1033#1]
W25Q16CV(SS)@SOIC8 [DX1044#1]
W25Q16CV@TFBGA24 [DX5146]
W25Q16DV(SN)@SOIC8 [DX1045#1]
W25Q16DV(ZP)@WSON8 [DX4005#1]
W25Q16DV@USON8 [DX4004#1]
W25Q16DW(SN)@SOIC8 [DX1045#1]
W25Q16DW(ZP)@WSON8 [DX4005#1]
W25Q16V(SF)@SOIC16 [DX1072#1]
W25Q16V(ZP)@WSON8 [DX4005#1]
W25Q20BW-SV8 [DX1045]
W25Q20BW-ZP8 [DX4005]
W25Q20CV-UX8 [DX4047]
W25D80(SN)@SOIC8 [DX1045]
W25D80(ZP)@WSON8 [DX4005]
W25N01GVZEIR@WSON8 [DX4006]
W25P10@SOIC8 [DX1045]
W25P16@MLP8(ISP) [DX0001]
W25P16@SOIC16(ISP) [DX0001]
W25P16@SOIC8(ISP) [DX0001]
W25P20@SOIC8 [DX1045#1]
W25P32@MLP8(ISP) [DX0001]
W25P32@SOIC16(ISP) [DX0001]
W25P40@SOIC8 [DX1045#1]
W25P64@MLP8(ISP) [DX0001]
W25P64@SOIC16(ISP) [DX0001]
W25P80@SOIC8 [DX1045#1]
W25Q05CV-SN8 [DX1045]
W25Q05CV-ZP8 [DX4005]
W25Q10CV-SN8 [DX1045]
W25Q10CV-ZP8 [DX4005]
W25Q128BV@WSON8 [DX4006#1]
W25Q128FV@SOIC16 [DX1033#1]
W25Q128FV@SON8 [DX4005#1]
W25Q128FV@TFBGA24[6*4] [DX5146]
W25Q128FV@WSON8 [DX4006#1]
W25Q128FW@SOIC16 [DX1033#1]
W25Q128FW@SON8 [DX4005#1]
W25Q128FW@TFBGA24[6*4] [DX5146]
W25Q128FW@WSON8 [DX4006#1]
W25Q16@MLP8(ISP) [DX0001]
W25Q16@SOIC16(ISP) [DX0001]
W25Q16@SOIC8(ISP) [DX0001]
W25Q16BV(SF)@SOIC16 [DX1072#1]
W25Q16BV(SS)@SOIC8 [DX1044#1]
W25Q16CL [DX0001]
W25Q16CL(SN)@SOIC8 [DX1045#1]
W25Q16CL(ZP)@WSON8 [DX4005#1]
W25Q16CV(SN)@SOIC8 [DX1045#1]
W25Q16CV(ZP)@WSON8 [DX4005#1]
W25Q16DV(SF)@SOIC16 [DX1033#1]
W25Q16DV(SS)@SOIC8 [DX1044#1]
W25Q16DV@TFBGA24 [DX5146]
W25Q16DW(SF)@SOIC16 [DX1033#1]
W25Q16DW(SS)@SOIC8 [DX1044#1]
W25Q16DW@TFBGA24 [DX5146]
W25Q16V(SS)@SOIC8 [DX1044#1]
W25Q20BW-SN8 [DX1045]
W25Q20BW-UX8 [DX4047]
W25Q20CV-SN8 [DX1045]
W25Q20CV-ZP8 [DX4005]

W25Q256FV@SOIC16 [DX1033#1]
W25Q256FV@TFBGA24[6*4] [DX5146]
W25Q257FV@SOIC16 [DX1033#1]
W25Q257FV@TFBGA24[6*4] [DX5146]
W25Q32@MLP8 [DX4005#1]
W25Q32@SOIC16 [DX1072#1]
W25Q32BV [DX0001#1]
W25Q32BV(SS)@SOIC8 [DX1044#1]
W25Q32BW(SF)@SOIC16 [DX1033#1]
W25Q32BW(SS)@SOIC8 [DX1044#1]
W25Q32DW(SF)@SOIC16 [DX1033#1]
W25Q32DW(SS)@SOIC8 [DX1044#1]
W25Q32DW(ZP)@WSON8 [DX4005#1]
W25Q32FV(SF)@SOIC16 [DX1033#1]
W25Q32FV(ST)@SOIC8 [DX1044#1]
W25Q32FV(ZP)@WSON8 [DX4005#1]
W25Q32FV@TFBGA24[6*4] [DX5146]
W25Q32FW(SF)@SOIC16 [DX1033#1]
W25Q32FW(ST)@SOIC8 [DX1044#1]
W25Q32FW(ZP)@WSON8 [DX4005#1]
W25Q32FW@TFBGA24[6*4] [DX5146]
W25Q32V(SS)@SOIC8 [DX1044#1]
W25Q40BL [DX0001]
W25Q40BL-SS8 [DX1044]
W25Q40BL-UX8 [DX4047]
W25Q40BV [DX0001]
W25Q40BV-SS8 [DX1044]
W25Q40BV-UX8 [DX4047]
W25Q40BW-SN8 [DX1045]
W25Q40BW-SV8 [DX1045]
W25Q40BW-ZP8 [DX4005]
W25Q40CL-SN8 [DX1045]
W25Q40CL-SV8 [DX1045]
W25Q40CL-ZP8 [DX4005]
W25Q40CV-SN8 [DX1045]
W25Q40CV-SV8 [DX1045]
W25Q40CV-ZP8 [DX4005]
W25Q64BV(SF)@SOIC16 [DX1072#1]
W25Q64BV(SF)@SOIC16(ISP) [DX0001]
W25Q64BV(SS)@SOIC8 [DX1044#1]
W25Q64BV(ZE)@WSON8 [DX4006#1]
W25Q64CV(SF)@SOIC16 [DX1033#1]
W25Q64CV(ZE)@WSON8 [DX4006#1]
W25Q64DW(SF)@SOIC16 [DX1033#1]
W25Q64DW(ZE)@WSON8 [DX4006#1]
W25Q64DW@TFBGA24 [DX5146]
W25Q64FJ(SF)@SOIC16 [DX1072#1]
W25Q64FJ(ST)@SOIC8 [DX1044#1]

W25Q256FV@TFBGA24[5*5] [DX5157]
W25Q256FV@WSON8 [DX4006#1]
W25Q257FV@TFBGA24[5*5] [DX5157]
W25Q257FV@WSON8 [DX4006#1]
W25Q32@MLP8(ISP) [DX0001]
W25Q32@SOIC16(ISP) [DX0001]
W25Q32BV(SF)@SOIC16 [DX1033#1]
W25Q32BV(ZP)@WSON8 [DX4005#1]
W25Q32BW(SN)@SOIC8 [DX1045#1]
W25Q32BW(ZP)@WSON8 [DX4005#1]
W25Q32DW(SN)@SOIC8 [DX1045#1]
W25Q32DW(ZE)@WSON8 [DX4006#1]
W25Q32FV [DX0001]
W25Q32FV(SS)@SOIC8 [DX1044#1]
W25Q32FV(ZE)@WSON8 [DX4006#1]
W25Q32FV@TFBGA24[5*5] [DX5157]
W25Q32FW [DX0001]
W25Q32FW(SS)@SOIC8 [DX1044#1]
W25Q32FW(ZE)@WSON8 [DX4006#1]
W25Q32FW@TFBGA24[5*5] [DX5157]
W25Q32V(SF)@SOIC16 [DX1072#1]
W25Q32V(ZP)@WSON8 [DX4005#1]
W25Q40BL-SN8 [DX1045]
W25Q40BL-SV8 [DX1045]
W25Q40BL-ZP8 [DX4005]
W25Q40BV-SN8 [DX1045]
W25Q40BV-SV8 [DX1045]
W25Q40BV-ZP8 [DX4005]
W25Q40BW-SS8 [DX1044]
W25Q40BW-UX8 [DX4047]
W25Q40CL [DX0001]
W25Q40CL-SS8 [DX1044]
W25Q40CL-UX8 [DX4047]
W25Q40CV [DX0001]
W25Q40CV-SS8 [DX1044]
W25Q40CV-UX8 [DX4047]
W25Q64BV [DX0001]
W25Q64BV(SS)@SOIC8(ISP) [DX0001]
W25Q64BV(ZE)@WSON8(ISP) [DX0001]
W25Q64CV(SS)@SOIC8 [DX1044#1]
W25Q64CV@TFBGA24 [DX5146]
W25Q64DW(SS)@SOIC8 [DX1044#1]
W25Q64DW(ZP)@WSON8 [DX4005#1]
W25Q64FJ [DX0001]
W25Q64FJ(SS)@SOIC8 [DX1044#1]
W25Q64FJ(ZE)@WSON8 [DX4006#1]

W25Q64FJ(ZP)@WSON8 [DX4005#1]
W25Q64FJ@TFBGA24(4*6) [DX5146]
W25Q64FJ@TFBGA24(5*5) [DX5157]
W25Q64FV [DX0001]
W25Q64FV(SF)@SOIC16 [DX1072#1]
W25Q64FV(SS)@SOIC8 [DX1044#1]
W25Q64FV(ST)@SOIC8 [DX1044#1]
W25Q64FV(ZE)@WSON8 [DX4006#1]
W25Q64FV(ZP)@WSON8 [DX4005#1]
W25Q64FV@TFBGA24(4*6) [DX5146]
W25Q64FV@TFBGA24(5*5) [DX5157]
W25Q64FW@SOIC8 [DX1044#1]
W25Q64FW@VSOP8 [DX1044#1]
W25Q64FW@WSON8 [DX4005#1]
W25Q80@MLP8 [DX4005#1]
W25Q80@SOIC8 [DX1045#1]
W25Q80BL [DX0001]
W25Q80BL@SOIC16 [DX1033#1]
W25Q80BL@SOIC8(150mil) [DX1045#1]
W25Q80BL@SOIC8(200mil) [DX1044#1]
W25Q80BL@USON8 [DX4047#1]
W25Q80BL@VSOP8(150mil) [DX1045#1]
W25Q80BL@VSOP8(200mil) [DX1044#1]
W25Q80BL@WSON8 [DX4005#1]
W25Q80BV [DX0001]
W25Q80BV@SOIC16 [DX1033#1]
W25Q80BV@SOIC8[4.0] [DX1045#1]
W25Q80BV@SOIC8[5.4] [DX1044#1]
W25Q80BV@WSON8 [DX4005#1]
W25Q80BW [DX0001]
W25Q80BW@SOIC16 [DX1033#1]
W25Q80BW@SOIC8[4.0] [DX1045#1]
W25Q80BW@SOIC8[5.4] [DX1044#1]
W25Q80BW@USON8 [DX4047#1]
W25Q80BW@VSOP8[4.0] [DX1045#1]
W25Q80BW@VSOP8[5.4] [DX1044#1]
W25Q80BW@WSON8 [DX4005#1]
W25Q80DW [DX0001]
W25Q80DW@SOIC16 [DX1033#1]
W25Q80DW@SOIC8[4.0] [DX1045#1]
W25Q80DW@SOIC8[5.4] [DX1044#1]
W25Q80DW@USON8 [DX1045#1]
W25Q80DW@VSOP8[4.0] [DX1045#1]
W25Q80DW@VSOP8[5.4] [DX1044#1]
W25Q80DW@WSON8 [DX4005#1]
W25X05CL-SD8 [DX1059]
W25X05CL-SN8 [DX1045]
W25X05CL-UX8 [DX4047]
W25X05CL-ZP8 [DX4005]
W25X10 [DX0001]
W25X10(SN)@SOIC8 [DX1045]
W25X10(SS)@SOIC8 [DX1044]
W25X10(ZP)@WSON8 [DX4005]
W25X10AL [DX0001]
W25X10AL-SN8 [DX1045]
W25X10AL-SS8 [DX1044]
W25X10AL-ZP8 [DX4005]
W25X10AV [DX0001]
W25X10AV(SN)@SOIC8 [DX1045]
W25X10AV(SS)@SOIC8 [DX1044]
W25X10AV(ZP)@WSON8 [DX4005]
W25X10BL [DX0001]
W25X10BL(SN)@SOIC8 [DX1045]
W25X10BL(SS)@SOIC8 [DX1044]
W25X10BL(ZP)@WSON8 [DX4005]
W25X10BV [DX0001]
W25X10BV(SN)@SOIC8 [DX1045]
W25X10BV(SS)@SOIC8 [DX1044]
W25X10BV(ZP)@WSON8 [DX4005]
W25X10BV-SD8 [DX1059]
W25X10BV-SV8 [DX1045]
W25X10BV-UX8 [DX4047]
W25X10CL-SD8 [DX1059]
W25X10CL-SN8 [DX1045]
W25X10CL-UX8 [DX4047]
W25X10CL-ZP8 [DX4005]
W25X10L [DX0001]
W25X10L(SN)@SOIC8 [DX1045]
W25X10L(ZP)@WSON8 [DX4005]
W25X10V [DX0001]
W25X10V(SN)@SOIC8 [DX1045]
W25X10V(SS)@SOIC8 [DX1044]
W25X10V(ZP)@WSON8 [DX4005]
W25X16@SOIC16 [DX1072#1]
W25X16@SOIC16(ISP) [DX0001]
W25X16@SOIC8 [DX1044#1]
W25X16@SOIC8(ISP) [DX0001]
W25X16AL [DX0001#1]
W25X16AL(SF)@SOIC16 [DX1072#1]
W25X16AL(SN)@SOIC8 [DX1045#1]
W25X16AL(SS)@SOIC8 [DX1044#1]

W25X16AL(ZP)@WSON8 [DX4005#1]
W25X16AV [DX0001#1]
W25X16AV(SF)@SOIC16 [DX1072#1]
W25X16AV(SN)@SOIC8 [DX1045#1]
W25X16AV(SS)@SOIC8 [DX1044#1]
W25X16AV(ZP)@WSON8 [DX4005#1]
W25X16BV [DX0001#1]
W25X16BV(SF)@SOIC16 [DX1072#1]
W25X16BV(SN)@SOIC8 [DX1045#1]
W25X16BV(SS)@SOIC8 [DX1044#1]
W25X16BV(ZP)@WSON8 [DX4005#1]
W25X16V [DX0001#1]
W25X16V(SF)@SOIC16 [DX1072#1]
W25X16V(SS)@SOIC8 [DX1044#1]
W25X16V(ZP)@WSON8 [DX4005#1]
W25X20 [DX0001]
W25X20(SN)@SOIC8 [DX1045]
W25X20(SS)@SOIC8 [DX1044]
W25X20(ZP)@WSON8 [DX4005]
W25X20AL [DX0001]
W25X20AL-SN8 [DX1045]
W25X20AL-SS8 [DX1044]
W25X20AL-ZP8 [DX4005]
W25X20AV [DX0001]
W25X20AV(SN)@SOIC8 [DX1045]
W25X20AV(SS)@SOIC8 [DX1044]
W25X20AV(ZP)@WSON8 [DX4005]
W25X20BL [DX0001]
W25X20BL(SN)@SOIC8 [DX1045]
W25X20BL(SS)@SOIC8 [DX1044]
W25X20BL(ZP)@WSON8 [DX4005]
W25X20BL-SV8 [DX1045]
W25X20BL-UX8 [DX4047]
W25X20BV [DX0001]
W25X20BV(SN)@SOIC8 [DX1045]
W25X20BV(SS)@SOIC8 [DX1044]
W25X20BV(ZP)@WSON8 [DX4005]
W25X20BV-UX8 [DX4047]
W25X20CL-SN8 [DX1045]
W25X20CL-SV8 [DX1045]
W25X20CL-UX8 [DX4047]
W25X20CL-ZP8 [DX4005]
W25X20CV-SN8 [DX1045]
W25X20CV-SV8 [DX1045]
W25X20CV-UX8 [DX4047]
W25X20CV-ZP8 [DX4005]
W25X20L [DX0001]
W25X20L(SN)@SOIC8 [DX1045]
W25X20L(ZP)@WSON8 [DX4005]
W25X20V [DX0001]
W25X20V(SN)@SOIC8 [DX1045]
W25X20V(SS)@SOIC8 [DX1044]
W25X20V(ZP)@WSON8 [DX4005]
W25X21CL@SOIC8 [DX1045]
W25X32@SOIC16 [DX1072#1]
W25X32@SOIC16(ISP) [DX0001]
W25X32@SOIC8 [DX1044#1]
W25X32@SOIC8(ISP) [DX0001]
W25X32AV(SF)@SOIC16 [DX1072#1]
W25X32AV(SS)@SOIC8 [DX1044#1]
W25X32AV(ZP)@WSON8 [DX4005#1]
W25X32V(SF)@SOIC16 [DX1072#1]
W25X32V(SS)@SOIC8 [DX1044#1]
W25X32V(ZP)@WSON8 [DX4005#1]
W25X40 [DX0001]
W25X40(SN)@SOIC8 [DX1045]
W25X40(SS)@SOIC8 [DX1044]
W25X40(ZP)@WSON8 [DX4005]
W25X40AL [DX0001]
W25X40AL(SN)@SOIC8 [DX1045]
W25X40AL(SS)@SOIC8 [DX1044]
W25X40AL(ZP)@WSON8 [DX4005]
W25X40AV [DX0001]
W25X40AV(SN)@SOIC8 [DX1045]
W25X40AV(SS)@SOIC8 [DX1044]
W25X40AV(ZP)@WSON8 [DX4005]
W25X40BL [DX0001]
W25X40BL(SN)@SOIC8 [DX1045]
W25X40BL(SS)@SOIC8 [DX1044]
W25X40BL(ZP)@WSON8 [DX4005]
W25X40BL-SV8 [DX1045]
W25X40BL-UX8 [DX4047]
W25X40BV [DX0001]
W25X40BV(SN)@SOIC8 [DX1045]
W25X40BV(SS)@SOIC8 [DX1044]
W25X40BV(ZP)@WSON8 [DX4005]
W25X40BV-SV8 [DX1045]
W25X40BV-UX8 [DX4047]
W25X40CL [DX0001]
W25X40CL-SN8 [DX1045]
W25X40CL-SS8 [DX1044]
W25X40CL-SV8 [DX1045]
W25X40CL-UX8 [DX4047]
W25X40CL-ZP8 [DX4005]
W25X40L [DX0001]
W25X40L(SN)@SOIC8 [DX1045]

W25X40L(SS)@SOIC8 [DX1044]
W25X40V [DX0001]
W25X40V(SS)@SOIC8 [DX1044]
W25X41CL@SOIC8 [DX1045]
W25X64@SOIC16(ISP) [DX0001]
W25X64@SOIC8(ISP) [DX0001]
W25X64BV(SS)@SOIC8 [DX1044#1]
W25X64V(SF)@SOIC16 [DX1072#1]
W25X64V(ZE)@WSON8 [DX4006#1]
W25X80(SN)@SOIC8 [DX1045]
W25X80(ZP)@WSON8 [DX4005]
W25X80AL-SN8 [DX1045]
W25X80AL-ZP8 [DX4005]
W25X80AV(SN)@SOIC8 [DX1045]
W25X80AV(ZP)@WSON8 [DX4005]
W25X80BL-SN8 [DX1045]
W25X80BL-ZP8 [DX4005]
W25X80L(SS)@SOIC8 [DX1044]
W25X80V [DX0001]
W25X80V(SS)@SOIC8 [DX1044]
W27C01 [DX0001]
W27C01@VSOP32 [DX1003]
W27C010@PLCC32 [DX2032]
W27C02 [DX0001]
W27C02@VSOP32 [DX1003]
W27C020@PLCC32 [DX2032]
W27C020M@PLCC32 [DX2032]
W27C257@PLCC32 [DX2032]
W27C4096@PLCC44 [DX2044]
W27C512 [DX0001]
W27C512@TSOP28 [DX1024]
W27C520@TSSOP20 [DX1000]
W27E01@PLCC32 [DX2032]
W27E010 [DX0001]
W27E010@SOIC32 [DX1034]
W27E02@PLCC32 [DX2032]
W27E020 [DX0001]
W27E040 [DX0001]
W27E040@SOIC32 [DX1034]
W27E257@PLCC32 [DX2032]
W27E4096 [DX0001]
W27E4096@TSOP40 [DX1006]
W27E512@PLCC32 [DX2032]
W27E520@SOIC20 [DX1033]
W27L01 [DX0001]
W27L01@VSOP32 [DX1003]
W27L010@PLCC32 [DX2032]
W27L02@PLCC32 [DX2032]
W25X40L(ZP)@WSON8 [DX4005]
W25X40V(SN)@SOIC8 [DX1045]
W25X40V(ZP)@WSON8 [DX4005]
W25X64@SOIC16 [DX1072#1]
W25X64@SOIC8 [DX1044#1]
W25X64BV(SF)@SOIC16 [DX1072#1]
W25X64BV(ZE)@WSON8 [DX4006#1]
W25X64V(SS)@SOIC8 [DX1044#1]
W25X80 [DX0001]
W25X80(SS)@SOIC8 [DX1044]
W25X80AL [DX0001]
W25X80AL-SS8 [DX1044]
W25X80AV [DX0001]
W25X80AV(SS)@SOIC8 [DX1044]
W25X80BL [DX0001]
W25X80BL-SS8 [DX1044]
W25X80L [DX0001]
W25X80L(ZP)@WSON8 [DX4005]
W25X80V(SN)@SOIC8 [DX1045]
W25X80V(ZP)@WSON8 [DX4005]
W27C01@PLCC32 [DX2032]
W27C010 [DX0001]
W27C010@SOIC32 [DX1034]
W27C02@PLCC32 [DX2032]
W27C020 [DX0001]
W27C020M [DX0001]
W27C257 [DX0001]
W27C4096 [DX0001]
W27C4096@TSOP40 [DX1006]
W27C512@PLCC32 [DX2032]
W27C520@SOIC20 [DX1033]
W27E01 [DX0001]
W27E01@VSOP32 [DX1003]
W27E010@PLCC32 [DX2032]
W27E02 [DX0001]
W27E02@VSOP32 [DX1003]
W27E020@PLCC32 [DX2032]
W27E040@PLCC32 [DX2032]
W27E257 [DX0001]
W27E400 [DX0001]
W27E4096@PLCC44 [DX2044]
W27E512 [DX0001]
W27E512@TSOP28 [DX1024]
W27E520@TSSOP20 [DX1000]
W27L01@PLCC32 [DX2032]
W27L010 [DX0001]
W27L02 [DX0001]
W27L02@VSOP32 [DX1003]

W27L520@SOIC20 [DX1033]
W27L520@TSSOP20 [DX1000]
W28F321BB@FBGA48 [DX5064]
W28F321BT@TSOP48 [DX1004]
W28F321TB@FBGA48 [DX5064]
W28F321TT@TSOP48 [DX1004]
W28F641BB@FBGA48 [DX5085]
W28F641BT@TSOP48 [DX1004]
W28F641TB@FBGA48 [DX5085]
W28F641TT@TSOP48 [DX1004]
W28J160BT@TSOP48 [DX1004]
W28J160TT@TSOP48 [DX1004]
W28J161BB@TFBGA48 [DX5085]
W28J161TB@TFBGA48 [DX5085]
W28J320BT@TSOP48 [DX1004]
W28J320TT@TSOP48 [DX1004]
W28J321BB@TFBGA48 [DX5085]
W28J321TB@TFBGA48 [DX5085]
W28J800BT@TSOP48 [DX1004]
W28J800TT@TSOP48 [DX1004]
W28V400BT@TSOP48 [DX1004]
W28V400TT@TSOP48 [DX1004]
W29C010 [DX0001]
W29C010@PLCC32 [DX2032]
W29C011A [DX0001]
W29C011A@PLCC32 [DX2032]
W29C020 [DX0001]
W29C020@PLCC32 [DX2032]
W29C020@SOIC32
W29C020@TSOP32 [DX1002]
W29C020C [DX0001]
W29C020C@PLCC32 [DX2032]
W29C020C@TSOP32 [DX1002]
W29C020C@VSOP32 [DX1003]
W29C040 [DX0001]
W29C040@PLCC32 [DX2032]
W29C040@TSOP32 [DX1002]
W29C040@VSOP32 [DX1003]
W29C101 [DX0001]
W29C101@PLCC44 [DX2044]
W29C101@TSOP40 [DX1006]
W29C102 [DX0001]
W29C102@PLCC44 [DX2044]
W29C102@TSOP40 [DX1006]
W29C102@VSOP40 [DX1005]
W29EE010 [DX0001]
W29EE010@PLCC32 [DX2032]
W29EE010@TSOP32 [DX1002]
W29EE011 [DX0001]
W29EE011@PLCC32 [DX2032]
W29EE011@TSOP32 [DX1002]
W29EE012 [DX0001]
W29EE012@PLCC32 [DX2032]
W29EE012@SOIC32 [DX1019]
W29EE512 [DX0001]
W29EE512@PLCC32 [DX2032]
W29EE512@TSOP32 [DX1002]
W29F040 [DX0001]
W29F040@PLCC32 [DX2032]
W29F040@TSOP32 [DX1002]
W29F102P@PLCC44 [DX2044]
W29F102Q@TSOP40 [DX1005]
W29GL032CB@FBGA48 [DX5002]
W29GL032CB@FBGA64 [DX5074]
W29GL032CB@TSOP48 [DX1004]
W29GL032CH@FBGA64 [DX5074]
W29GL032CH@TSOP56 [DX1011]
W29GL032CL@FBGA64 [DX5074]
W29GL032CL@TSOP56 [DX1011]
W29GL032CT@FBGA48 [DX5002]
W29GL032CT@FBGA64 [DX5074]
W29GL032CT@TSOP48 [DX1004]
W29GL064CB@FBGA48 [DX5002]
W29GL064CB@FBGA64 [DX5074]
W29GL064CB@TSOP48 [DX1004]
W29GL064CH@FBGA64 [DX5074]
W29GL064CH@TSOP56 [DX1011]
W29GL064CL@FBGA64 [DX5074]
W29GL064CL@TSOP56 [DX1011]
W29GL064CT@FBGA48 [DX5002]
W29GL064CT@FBGA64 [DX5074]
W29GL064CT@TSOP48 [DX1004]
W29GL128CH@FBGA64 [DX5074]
W29GL128CH@TSOP56 [DX1011]
W29GL128CL@FBGA64 [DX5074]
W29GL128CL@TSOP56 [DX1011]
W29GL256PH9B@FBGA64 [DX5074]
W29GL256PH9T@TSOP56 [DX1011]
W29GL256PL9B@FBGA64 [DX5074]
W29GL256PL9T@TSOP56 [DX1011]
W29GL256SH9B@FBGA64 [DX5103]
W29GL256SH9C@FBGA56 [DX5045]
W29GL256SH9T@TSOP56 [DX1011]
W29GL256SL9B@FBGA64 [DX5103]
W29GL256SL9C@FBGA56 [DX5045]
W29GL256SL9T@TSOP56 [DX1011]

W29L102P@PLCC44 [DX2044]
W29N01GVDIAA@BGA48 [DX5246-1]
W29N01GVSIAA@TSOP48 [DX1004-3]
W29N02GVSIAA@TSOP48 [DX1004-3]
W39F010@PLCC32 [DX2032]
W39F010@TSOP32[18.4mm] [DX1002]
W39L010@TSOP32 [DX1003]
W39L020@TSOP32[12.4mm] [DX1003]
W39L040@PLCC32 [DX2032]
W39L040@TSOP32[18.4mm] [DX1002]
W39L040A@PLCC32 [DX2032]
W39L040A@VSOP32 [DX1003]
W39L512@TSOP32 [DX1003]
W39V040AQ@VSOP32 [DX1003]
W39V040B(Q)@VSOP32 [DX1003]
W39V040CPZ@PLCC32 [DX2032]
W39V040CQZ@VSOP32 [DX1003]
W39V040FAQ@VSOP32 [DX1003]
W39V040FB(P)@PLCC32 [DX2032]
W39V040FCP@PLCC32 [DX2032]
W39V040FCQ@VSOP32 [DX1003]
W39V080A(P)@PLCC32 [DX2032]
W39V080A(T)@TSOP40 [DX1006]
W39V080FA(Q)@VSOP32 [DX1003]
W45B012@PLCC32 [DX2032]
W45B512@PLCC32 [DX2032]
W49F002 [DX0001]
W49F002@TSOP32 [DX1002]
W49F002B@PLCC32 [DX2032]
W49F002N [DX0001]
W49F002N@TSOP32 [DX1002]
W49F002U@PLCC32 [DX2032]
W49F020 [DX0001]
W49F020@TSOP32 [DX1002]
W49F102Q@TSOP40 [DX1005]
W49F201T@TSOP48 [DX1004]
W49L102Q@TSOP40 [DX1005]
W49L201T@TSOP48 [DX1004]
W49L401T@TSOP48 [DX1004]
W49V002A@VSOP32 [DX1003]
W49V002FA@VSOP32 [DX1003]
W49V002FP@VSOP32 [DX1003]
W49V002P@VSOP32 [DX1003]
W55F10A [DX0001]
W29L102Q@TSOP40 [DX1005]
W29N01GVSCAA@TSOP48 [DX1004-3]
W29N02GVBIAA@BGA63 [DX5046-1]
W39F010 [DX0001]
W39F010@TSOP32[12.4mm] [DX1003]
W39L010@PLCC32 [DX2032]
W39L020@PLCC32 [DX2032]
W39L020@TSOP32[18.4mm] [DX1002]
W39L040@TSOP32[12.4mm] [DX1003]
W39L040A [DX0001]
W39L040A@TSOP32 [DX1002]
W39L512@PLCC32 [DX2032]
W39V040AP@PLCC32 [DX2032]
W39V040B(P)@PLCC32 [DX2032]
W39V040CP@PLCC32 [DX2032]
W39V040CQ@VSOP32 [DX1003]
W39V040FAP@PLCC32 [DX2032]
W39V040FAT@TSOP40 [DX1006]
W39V040FB(Q)@VSOP32 [DX1003]
W39V040FCPZ@PLCC32 [DX2032]
W39V040FCQZ@VSOP32 [DX1003]
W39V080A(Q)@VSOP32 [DX1003]
W39V080FA(P)@PLCC32 [DX2032]
W39V080FA(T)@TSOP40 [DX1006]
W45B012@SON8 [DX4005]
W45B512@SON8 [DX4005]
W49F002@PLCC32 [DX2032]
W49F002B [DX0001]
W49F002B@TSOP32 [DX1002]
W49F002N@PLCC32 [DX2032]
W49F002U [DX0001]
W49F002U@TSOP32 [DX1002]
W49F020@PLCC32 [DX2032]
W49F102P@PLCC44 [DX2044]
W49F201S@PSOP44 [DX1014]
W49L102P@PLCC44 [DX2044]
W49L201S@PSOP44 [DX1014]
W49L401S@PSOP44 [DX1014]
W49V002A@PLCC32 [DX2032]
W49V002FA@PLCC32 [DX2032]
W49V002FP@PLCC32 [DX2032]
W49V002P@PLCC32 [DX2032]
W55F05 [DX0001]
W55F20 [DX0001]

MICROCONTROLLER

N79E342AKG [DX0001]
N79E342ASG@SOP16 [DX1033]
N79E342RAKG [DX0001]
N79E342RASG@SOP16 [DX1033]
N79E352AEG [DX0001]
N79E352AFG@TQFP44 [DX3002]
N79E352ALG@TQFP48 [DX3007]
N79E352APG@PLCC44 [DX2044]
N79E8213AKG [DX0001]
N79E8213ASG@SOP20 [DX1033]
N79E8213RAKG [DX0001]
N79E8213RASG@SOP20 [DX1033]
W77E058A [DX0001]
W77E058A@PLCC44 [DX2044]
W77E058A@TQFP44 [DX3002]
W77E468@QFP100 [DX3023]
W77E516 [DX0001]
W77E516@PLCC44 [DX2044]
W77E516@TQFP44 [DX3002]
W77E532 [DX0001]
W77E532@PLCC44 [DX2044]
W77E532@TQFP44 [DX3002]
W77E532A [DX0001]
W77E532A@PLCC44 [DX2044]
W77E532A@TQFP44 [DX3002]
W77E58 [DX0001]
W77E58@PLCC44 [DX2044]
W77E58@TQFP44 [DX3002]
W77IE58 [DX0001]
W77IE58@PLCC44 [DX2044]
W77IE58@TQFP44 [DX3002]
W77L058A [DX0001]
W77L058A@PLCC44 [DX2044]
W77L058A@TQFP44 [DX3002]
W77L516A [DX0001]
W77L516A@PLCC44 [DX2044]
W77L516A@TQFP44 [DX3002]
W77L532A [DX0001]
W77L532A@PLCC44 [DX2044]
W77L532A@TQFP44 [DX3002]
W77LE516 [DX0001]
W77LE516@PLCC44 [DX2044]
W77LE516@TQFP44 [DX3002]
W77LE532 [DX0001]
W77LE532@PLCC44 [DX2044]
W77LE532@TQFP44 [DX3002]
W77LE58 [DX0001]
W77LE58@PLCC44 [DX2044]
W77LE58@TQFP44 [DX3002]
W77LE58A [DX0001]
W77LE58A@PLCC44 [DX2044]
W77LE58A@TQFP44 [DX3002]
W78E051B [DX0001]
W78E051B@PLCC44 [DX2044]
W78E051B@TQFP44 [DX3002]
W78E051C [DX0001]
W78E051C@PLCC44 [DX2044]
W78E051C@TQFP44 [DX3002]
W78E051DDG [DX0001]
W78E051DFG@PQFP44 [DX3002]
W78E051DLG@LQFP48 [DX3007]
W78E051DPG@PLCC44 [DX2044]
W78E052B [DX0001]
W78E052B@PLCC44 [DX2044]
W78E052B@TQFP44 [DX3002]
W78E052C [DX0001]
W78E052C@PLCC44 [DX2044]
W78E052C@TQFP44 [DX3002]
W78E052DDG [DX0001]
W78E052DFG@PQFP44 [DX3002]
W78E052DLG@LQFP48 [DX3007]
W78E052DPG@PLCC44 [DX2044]
W78E054B [DX0001]
W78E054B@PLCC44 [DX2044]
W78E054B@TQFP44 [DX3002]
W78E054C [DX0001]
W78E054C@PLCC44 [DX2044]
W78E054C@TQFP44 [DX3002]
W78E054DDG [DX0001]
W78E054DFG@PQFP44 [DX3002]
W78E054DLG@LQFP48 [DX3007]
W78E054DPG@PLCC44 [DX2044]
W78E058B [DX0001]
W78E058B@PLCC44 [DX2044]
W78E058B@TQFP44 [DX3002]
W78E058DDG [DX0001]
W78E058DFG@TQFP44 [DX3002]
W78E058DLG@TQFP48 [DX3007]
W78E058DPG@PLCC44 [DX2044]
W78E065 [DX0001]
W78E065@PLCC44 [DX2044]
W78E065@TQFP44 [DX3002]
W78E354(dip40) [DX0001]
W78E354(dip48) [DX0001]
W78E354@PLCC68 [DX2068]
W78E365 [DX0001]

W78E365@PLCC44 [DX2044]
W78E365@TQFP44 [DX3002]
W78E365A [DX0001]
W78E365A@PLCC44 [DX2044]
W78E365A@TQFP44 [DX3002]
W78E374B [DX0001]
W78E378 [DX0001]
W78E378E [DX0001]
W78E378P@PLCC44 [DX2044]
W78E51 [DX0001]
W78E51@PLCC44 [DX2044]
W78E51@TQFP44 [DX3002]
W78E516 [DX0001]
W78E516@PLCC44 [DX2044]
W78E516@TQFP44 [DX3002]
W78E516B [DX0001]
W78E516B@PLCC44 [DX2044]
W78E516B@TQFP44 [DX3002]
W78E516DDG [DX0001]
W78E516DFG@TQFP44 [DX3002]
W78E516DLG@TQFP48 [DX3007]
W78E516DPG@PLCC44 [DX2044]
W78E51B [DX0001]
W78E51B@PLCC44 [DX2044]
W78E51B@PQFP44 [DX3002]
W78E51B@TQFP44 [DX3003]
W78E51C [DX0001]
W78E51C@PLCC44 [DX2044]
W78E51C@TQFP44 [DX3002]
W78E52 [DX0001]
W78E52@PLCC44 [DX2044]
W78E52@TQFP44 [DX3002]
W78E52B [DX0001]
W78E52B@PLCC44 [DX2044]
W78E52B@TQFP44 [DX3002]
W78E52C [DX0001]
W78E52C@PLCC44 [DX2044]
W78E52C@TQFP44 [DX3002]
W78E54 [DX0001]
W78E54@PLCC44 [DX2044]
W78E54@PQFP44 [DX3002]
W78E54@TQFP44 [DX3003]
W78E54B [DX0001]
W78E54B@PLCC44 [DX2044]
W78E54B@TQFP44 [DX3002]
W78E54C [DX0001]
W78E54C@PLCC44 [DX2044]
W78E54C@TQFP44 [DX3002]
W78E58 [DX0001]
W78E58@PLCC44 [DX2044]
W78E58@PQFP44 [DX3002]
W78E58@TQFP44 [DX3003]
W78E58B [DX0001]
W78E58B@PLCC44 [DX2044]
W78E58B@TQFP44 [DX3002]
W78E62B [DX0001]
W78E62B@PLCC44 [DX2044]
W78E62B@TQFP44 [DX3002]
W78E65 [DX0001]
W78E65@PLCC44 [DX2044]
W78E65@TQFP44 [DX3002]
W78E858 [DX0001]
W78E858@PLCC44 [DX2044]
W78E858@TQFP44 [DX3002]
W78ERD2 [DX0001]
W78ERD2@PLCC44 [DX2044]
W78ERD2@TQFP44 [DX3002]
W78I051DDG [DX0001]
W78I051DFG@PQFP44 [DX3002]
W78I051DLG@LQFP48 [DX3007]
W78I051DPG@PLCC44 [DX2044]
W78I052 [DX0001]
W78I052@PLCC44 [DX2044]
W78I052DDG [DX0001]
W78I052DFG@PQFP44 [DX3002]
W78I052DLG@LQFP48 [DX3007]
W78I052DPG@PLCC44 [DX2044]
W78I054 [DX0001]
W78I054@PLCC44 [DX2044]
W78I054DDG [DX0001]
W78I054DFG@PQFP44 [DX3002]
W78I054DLG@LQFP48 [DX3007]
W78I054DPG@PLCC44 [DX2044]
W78IE52 [DX0001]
W78IE52@PLCC44 [DX2044]
W78IE54 [DX0001]
W78IE54@PLCC44 [DX2044]
W78IRD2 [DX0001]
W78IRD2@PLCC44 [DX2044]
W78IRD2@TQFP44 [DX3002]
W78L051A [DX0001]
W78L051A@PLCC44 [DX2044]
W78L051A@TQFP44 [DX3002]
W78L051C [DX0001]
W78L051C@PLCC44 [DX2044]
W78L051C@TQFP44 [DX3002]

W78L052A [DX0001]
W78L052A@PLCC44 [DX2044]
W78L052A@TQFP44 [DX3002]
W78L052C [DX0001]
W78L052C@PLCC44 [DX2044]
W78L052C@TQFP44 [DX3002]
W78L054A [DX0001]
W78L054A@PLCC44 [DX2044]
W78L054A@TQFP44 [DX3002]
W78L054C [DX0001]
W78L054C@PLCC44 [DX2044]
W78L054C@TQFP44 [DX3002]
W78L058A [DX0001]
W78L058A@PLCC44 [DX2044]
W78L058A@TQFP44 [DX3002]
W78L365 [DX0001]
W78L365@PLCC44 [DX2044]
W78L365@TQFP44 [DX3002]
W78L365@TQFP48 [DX3007]
W78L365A [DX0001]
W78L365A@PLCC44 [DX2044]
W78L365A@TQFP44 [DX3002]
W78L365A@TQFP48 [DX3007]
W78L516 [DX0001]
W78L516@PLCC44 [DX2044]
W78L516@TQFP44 [DX3002]
W78L516A [DX0001]
W78L516A@PLCC44 [DX2044]
W78L516A@TQFP44 [DX3002]
W78L812A [DX0001]
W78L812A@PLCC44 [DX2044]
W78L812A@TQFP44 [DX3002]
W78LE365 [DX0001]
W78LE365@PLCC44 [DX2044]
W78LE365@TQFP44 [DX3002]
W78LE365@TQFP48 [DX3007]
W78LE51 [DX0001]
W78LE51@PLCC44 [DX2044]
W78LE51@TQFP44 [DX3002]
W78LE516 [DX0001]
W78LE516@PLCC44 [DX2044]
W78LE516@TQFP44 [DX3002]
W78LE51C [DX0001]
W78LE51C@PLCC44 [DX2044]
W78LE51C@TQFP44 [DX3002]
W78LE52 [DX0001]
W78LE52@PLCC44 [DX2044]
W78LE52@TQFP44 [DX3002]
W78LE52C [DX0001]
W78LE52C@PLCC44 [DX2044]
W78LE52C@TQFP44 [DX3002]
W78LE54 [DX0001]
W78LE54@PLCC44 [DX2044]
W78LE54@TQFP44 [DX3002]
W78LE54C [DX0001]
W78LE54C@PLCC44 [DX2044]
W78LE54C@TQFP44 [DX3002]
W78LE58 [DX0001]
W78LE58@PLCC44 [DX2044]
W78LE58@TQFP44 [DX3002]
W78LE812 [DX0001]
W78LE812@PLCC44 [DX2044]
W78LE812@TQFP44 [DX3002]
W79E201@PLCC44 [DX2044]
W79E201@TQFP44 [DX3002]
W79E2051(dip14) [DX0001]
W79E2051(dip16) [DX0001]
W79E2051(dip20) [DX0001]
W79E2051@SOIC14 [DX1033]
W79E2051@SOIC16 [DX1033]
W79E2051@SOIC20 [DX1033]
W79E2051R(dip20) [DX0001]
W79E2051R@SOIC20 [DX1033]
W79E216AFG@PQFP100 [DX3023]
W79E217AFG@PQFP100 [DX3023]
W79E225ALG@TQFP48 [DX3007]
W79E225APG@PLCC44 [DX2044]
W79E226ALG@TQFP48 [DX3007]
W79E226APG@PLCC44 [DX2044]
W79E227ALG@TQFP48 [DX3007]
W79E227APG@PLCC44 [DX2044]
W79E4051(dip14) [DX0001]
W79E4051(dip16) [DX0001]
W79E4051(dip20) [DX0001]
W79E4051@SOIC14 [DX1033]
W79E4051@SOIC16 [DX1033]
W79E4051@SOIC20 [DX1033]
W79E4051R(dip20) [DX0001]
W79E4051R@SOIC20 [DX1033]
W79E532 [DX0001]
W79E532@PLCC44 [DX2044]
W79E532@TQFP44 [DX3002]
W79E532A [DX0001]
W79E532A@PLCC44 [DX2044]
W79E532A@TQFP44 [DX3002]
W79E533A@PLCC44 [DX2044]

W79E549A@PLCC68 [DX2068]
W79E632@PLCC44 [DX2044]
W79E632A [DX0001]
W79E632A@TQFP44 [DX3002]
W79E648A@PLCC68 [DX2068]
W79E658A@PQFP100 [DX3023]
W79E801A [DX0001]
W79E802A [DX0001]
W79E803A [DX0001]
W79E804A [DX0001]
W79E821A [DX0001]
W79E822A [DX0001]
W79E822B [DX0001]
W79E823A [DX0001]
W79E823B [DX0001]
W79E824A [DX0001]
W79E825A [DX0001]
W79E831A [DX0001]
W79E832A [DX0001]
W79E833A [DX0001]
W79E834A [DX0001]
W79L532 [DX0001]
W79L532@TQFP44 [DX3002]
W79L632 [DX0001]
W79L632@TQFP44 [DX3002]
W79L632A@PLCC44 [DX2044]
W79L633A@PLCC44 [DX2044]
W79L649A@PLCC68 [DX2068]
W79L659A@QFP100 [DX3023]
W83L950D@TQFP80 [DX3016]
W83L951ADG@LQFP128 [DX3030]
W83L951DF@QFP128 [DX30UN]
W83L951F@QFP128 [DX30UN]
W99100DG@TQFP48 [DX3007]
W79E632 [DX0001]
W79E632@TQFP44 [DX3002]
W79E632A@PLCC44 [DX2044]
W79E633A@PLCC44 [DX2044]
W79E649A@PLCC68 [DX2068]
W79E659A@QFP100 [DX3023]
W79E801A@SOIC20 [DX1033]
W79E802A@SOIC20 [DX1033]
W79E803A@SOIC20 [DX1033]
W79E804A@SOIC20 [DX1033]
W79E821A@SOIC20 [DX1033]
W79E822A@SOIC20 [DX1033]
W79E822B@SOIC20 [DX1033]
W79E823A@SOIC20 [DX1033]
W79E823B@SOIC20 [DX1033]
W79E824A@SOIC20 [DX1033]
W79E825A@SOIC20 [DX1033]
W79E831A@SOIC28 [DX1033]
W79E832A@SOIC28 [DX1033]
W79E833A@SOIC28 [DX1033]
W79E834A@SOIC28 [DX1033]
W79L532@PLCC44 [DX2044]
W79L549A@PLCC68 [DX2068]
W79L632@PLCC44 [DX2044]
W79L632A [DX0001]
W79L632A@TQFP44 [DX3002]
W79L648A@PLCC68 [DX2068]
W79L658A@PQFP100 [DX3023]
W83960G@LQFP64 [DX3011]
W83L950G@TQFP80 [DX3016]
W83L951D@LQFP128 [DX3030]
W83L951DG@LQFP128 [DX3030]
W925EP01@PQFP100 [DX3023]

WING Shing

E(E)PROM/FRAM/NVRAM

WS24C02 [DX0001]
WS24C04 [DX0001]
WS24C08 [DX0001]
WS24C16 [DX0001]
WS24W04 [DX0001]
WS24W08 [DX0001]
WS24W16 [DX0001]
WS24C02@SOP8 [DX1045]
WS24C04@SOP8 [DX1045]
WS24C08@SOP8 [DX1045]
WS24C16@SOP8 [DX1045]
WS24W04@SOP8 [DX1045]
WS24W08@SOP8 [DX1045]
WS24W16@SOP8 [DX1045]

WSI

E(E)PROM/FRAM/NVRAM

WS27C010L [DX0001]
WS27C010L@TSOP32 [DX1002]
WS27C010R@PLCC32 [DX2032]
WS27C040L [DX0001]
WS27C040L@TSOP32 [DX1002]
WS27C128F@PLCC32 [DX2032]
WS27C128L@PLCC32 [DX2032]
WS27C210L@PLCC44 [DX2044]
WS27C256F@PLCC32 [DX2032]
WS27C256L@PLCC32 [DX2032]
WS27C512F@PLCC32 [DX2032]
WS27C512L@PLCC32 [DX2032]
WS27C64@PLCC32 [DX2032]
WS27C64F@PLCC32 [DX2032]
WS27C64L@PLCC32 [DX2032]
WS57C128@PLCC32 [DX2032]
WS57C128F@PLCC32 [DX2032]
WS57C128FB@PLCC32 [DX2032]
WS57C191@PLCC28 [DX2028]
WS57C191B@PLCC28 [DX2028]
WS57C191C@PLCC28 [DX2028]
WS57C256F@PLCC32 [DX2032]
WS57C256FB@PLCC32 [DX2032]
WS57C257@PLCC44 [DX2044]
WS57C291@PLCC28 [DX2028]
WS57C291B@PLCC28 [DX2028]
WS57C291C@PLCC28 [DX2028]
WS57C43@PLCC28 [DX2028]
WS57C43B@PLCC28 [DX2028]
WS57C43C@PLCC28 [DX2028]
WS57C45@PLCC28 [DX2028]
WS57C49@PLCC28 [DX2028]
WS57C49B@PLCC28 [DX2028]
WS57C49C@PLCC28 [DX2028]
WS57C51@PLCC32 [DX2032]
WS57C51B@PLCC32 [DX2032]
WS57C51C@PLCC32 [DX2032]
WS57C64F@PLCC32 [DX2032]
WS57C71C@PLCC32 [DX2032]
WS57LV191C@PLCC28 [DX2028]
WS57LV291C@PLCC28 [DX2028]
WS27C010L@PLCC32 [DX2032]
WS27C010R [DX0001]
WS27C010R@TSOP32 [DX1002]
WS27C040L@PLCC32 [DX2032]
WS27C128F [DX0001]
WS27C128L [DX0001]
WS27C210L [DX0001]
WS27C256F [DX0001]
WS27C256L [DX0001]
WS27C512F [DX0001]
WS27C512L [DX0001]
WS27C64 [DX0001]
WS27C64F [DX0001]
WS27C64L [DX0001]
WS57C128 [DX0001]
WS57C128F [DX0001]
WS57C128FB [DX0001]
WS57C191 [DX0001]
WS57C191B [DX0001]
WS57C191C [DX0001]
WS57C256F [DX0001]
WS57C256FB [DX0001]
WS57C257 [DX0001]
WS57C291 [DX0001]
WS57C291B [DX0001]
WS57C291C [DX0001]
WS57C43 [DX0001]
WS57C43B [DX0001]
WS57C43C [DX0001]
WS57C45 [DX0001]
WS57C49 [DX0001]
WS57C49B [DX0001]
WS57C49C [DX0001]
WS57C51 [DX0001]
WS57C51B [DX0001]
WS57C51C [DX0001]
WS57C64F [DX0001]
WS57C71C [DX0001]
WS57LV191C [DX0001]
WS57LV291C [DX0001]

MICROCONTROLLER

PSD211R@PLCC44 [DX2044]
PSD211R@TQFP44 [DX3003]
PSD301@PLCC44 [DX2044]
PSD301@TQFP44 [DX3003]
PSD301B@PLCC44 [DX2044]
PSD301C1@PLCC44 [DX2044]
PSD301L@PLCC44 [DX2044]
PSD301L@TQFP44 [DX3003]
PSD301R@PLCC44 [DX2044]
PSD301R@TQFP44 [DX3003]
PSD301RV@PLCC44 [DX2044]
PSD301V@PLCC44 [DX2044]
PSD302@PLCC44 [DX2044]
PSD302@TQFP44 [DX3003]
PSD302B@PLCC44 [DX2044]
PSD302B@PLCC44(USA) [DX2044]
PSD302C1@PLCC44 [DX2044]
PSD302L@PLCC44 [DX2044]
PSD302L@TQFP44 [DX3003]
PSD302R@PLCC44 [DX2044]
PSD302R@TQFP44 [DX3003]
PSD302RV@PLCC44 [DX2044]
PSD302V@PLCC44 [DX2044]
PSD303@PLCC44 [DX2044]
PSD303@TQFP44 [DX3003]
PSD303C1@PLCC44 [DX2044]
PSD303L@PLCC44 [DX2044]
PSD303L@TQFP44 [DX3003]
PSD303R@PLCC44 [DX2044]
PSD303R@TQFP44 [DX3003]
PSD303RV@PLCC44 [DX2044]
PSD303V@PLCC44 [DX2044]
PSD311@PLCC44 [DX2044]
PSD311@TQFP44 [DX3003]
PSD311B@PLCC44 [DX2044]
PSD311C1@PLCC44 [DX2044]
PSD311L@PLCC44 [DX2044]
PSD311L@TQFP44 [DX3003]
PSD311R@PLCC44 [DX2044]
PSD311R@TQFP44 [DX3003]
PSD311RV@PLCC44 [DX2044]
PSD311V@PLCC44 [DX2044]
PSD312@PLCC44 [DX2044]
PSD312@TQFP44 [DX3046]
PSD312B@PLCC44 [DX2044]
PSD312C1@PLCC44 [DX2044]
PSD312L@PLCC44 [DX2044]
PSD312L@TQFP44 [DX3046]
PSD312R@PLCC44 [DX2044]
PSD312R@TQFP44 [DX3046]
PSD312RV@PLCC44 [DX2044]
PSD312V@PLCC44 [DX2044]
PSD313@PLCC44 [DX2044]
PSD313@TQFP44 [DX3003]
PSD313-B@PLCC44 [DX2044]
PSD313-B@TQFP44 [DX3003]
PSD313C1@PLCC44 [DX2044]
PSD313L@PLCC44 [DX2044]
PSD313L@TQFP44 [DX3003]
PSD313R@PLCC44 [DX2044]
PSD313R@TQFP44 [DX3003]
PSD313RV@PLCC44 [DX2044]
PSD313V@PLCC44 [DX2044]
PSD813F1@PLCC52 [DX2052]
PSD813F1@QFP52 [DX3010]
PSD813F1@QFP52(*) [DX3010]
PSD813F1A@PLCC52 [DX2052]
PSD813F1V@PLCC52 [DX2052]
PSD813F1V@QFP52 [DX3010]
PSD813F1V@QFP52(*) [DX3010]
PSD813F1VA@PLCC52 [DX3010]
PSD813F2@PLCC52 [DX2052]
PSD813F2@TQFP52 [DX3010]
PSD813F2@TQFP52(*) [DX3010]
PSD813F2A@PLCC52 [DX2052]
PSD813F2V@PLCC52 [DX2052]
PSD813F2V@TQFP52 [DX3010]
PSD813F2V@TQFP52(*) [DX3010]
PSD813F2VA@PLCC52 [DX2052]
PSD813F4@PLCC52 [DX2052]
PSD813F4@TQFP52 [DX3010]
PSD813F4@TQFP52(*) [DX3010]
PSD813F4V@PLCC52 [DX2052]
PSD813F4V@TQFP52 [DX3010]
PSD813F4V@TQFP52(*) [DX3010]
PSD833F2@PLCC52 [DX2052]
PSD833F2@PQFP52 [DX3010]
PSD833F2@TQFP52(*) [DX3010]
PSD833F2V@PLCC52 [DX2052]
PSD833F2V@TQFP52 [DX3010]
PSD833F2V@TQFP52(*) [DX3010]
PSD834F2@PLCC52 [DX2052]

PSD834F2@PLCC52(new) [DX2052]
PSD834F2@TQFP52(new) [DX3009]
PSD834F2V@PLCC52(new) [DX2052]
PSD834F2V@TQFP52(new) [DX3009]
PSD853F2@PQFP52 [DX3010]
PSD853F2V@PLCC52 [DX2052]
PSD853F2V@TQFP52(*) [DX3010]
PSD854F2@PLCC52(new) [DX2052]
PSD854F2@TQFP52(new) [DX3009]
PSD854F2V@PLCC52(new) [DX2052]
PSD854F2V@TQFP52(new) [DX3009]
ZPSD211R@TQFP44 [DX3003]
ZPSD211RV@TQFP44 [DX3003]
ZPSD301@TQFP44 [DX3003]
ZPSD301L@TQFP44 [DX3003]
ZPSD301R@TQFP44 [DX3003]
ZPSD301RL@TQFP44 [DX3003]
ZPSD301RV@TQFP44 [DX3003]
ZPSD301V@TQFP44 [DX3003]
ZPSD302@TQFP44 [DX3003]
ZPSD302B@PLCC44(USA) [DX2044]
ZPSD302L@TQFP44 [DX3003]
ZPSD302R@TQFP44 [DX3003]
ZPSD302RL@TQFP44 [DX3003]
ZPSD302RV@TQFP44 [DX3003]
ZPSD302V@TQFP44 [DX3003]
ZPSD303@TQFP44 [DX3003]
ZPSD303L@TQFP44 [DX3003]
ZPSD303R@TQFP44 [DX3003]
ZPSD303RL@TQFP44 [DX3003]
ZPSD303RV@TQFP44 [DX3003]
ZPSD303V@TQFP44 [DX3003]
ZPSD311@TQFP44 [DX3003]
ZPSD311L@TQFP44 [DX3003]
ZPSD311R@TQFP44 [DX3003]
ZPSD311RL@TQFP44 [DX3003]
ZPSD311RV@TQFP44 [DX3003]
ZPSD311V@TQFP44 [DX3003]
ZPSD312@TQFP44 [DX3046]
ZPSD312L@PLCC44 [DX2044]
ZPSD312R@PLCC44 [DX2044]
ZPSD312RL@PLCC44 [DX2044]
ZPSD312RV@PLCC44 [DX2044]
ZPSD312V@PLCC44 [DX2044]
ZPSD313@PLCC44 [DX2044]
ZPSD313L@PLCC44 [DX2044]
ZPSD313R@PLCC44 [DX2044]
ZPSD313RL@PLCC44 [DX2044]
PSD834F2@TQFP52 [DX3009]
PSD834F2V@PLCC52 [DX2052]
PSD834F2V@TQFP52 [DX3009]
PSD853F2@PLCC52 [DX2052]
PSD853F2@TQFP52(*) [DX3010]
PSD853F2V@TQFP52 [DX3010]
PSD854F2@PLCC52 [DX2052]
PSD854F2@TQFP52 [DX3009]
PSD854F2V@PLCC52 [DX2052]
PSD854F2V@TQFP52 [DX3009]
ZPSD211R@PLCC44 [DX2044]
ZPSD211RV@PLCC44 [DX2044]
ZPSD301@PLCC44 [DX2044]
ZPSD301L@PLCC44 [DX2044]
ZPSD301R@PLCC44 [DX2044]
ZPSD301RL@PLCC44 [DX2044]
ZPSD301RV@PLCC44 [DX2044]
ZPSD301V@PLCC44 [DX2044]
ZPSD302@PLCC44 [DX2044]
ZPSD302B@PLCC44 [DX2044]
ZPSD302L@PLCC44 [DX2044]
ZPSD302R@PLCC44 [DX2044]
ZPSD302RL@PLCC44 [DX2044]
ZPSD302RV@PLCC44 [DX2044]
ZPSD302V@PLCC44 [DX2044]
ZPSD303@PLCC44 [DX2044]
ZPSD303L@PLCC44 [DX2044]
ZPSD303R@PLCC44 [DX2044]
ZPSD303RL@PLCC44 [DX2044]
ZPSD303RV@PLCC44 [DX2044]
ZPSD303V@PLCC44 [DX2044]
ZPSD311@PLCC44 [DX2044]
ZPSD311L@PLCC44 [DX2044]
ZPSD311R@PLCC44 [DX2044]
ZPSD311RL@PLCC44 [DX2044]
ZPSD311RV@PLCC44 [DX2044]
ZPSD311V@PLCC44 [DX2044]
ZPSD312@PLCC44 [DX2044]
ZPSD312B@PLCC44 [DX2044]
ZPSD312L@TQFP44 [DX3046]
ZPSD312R@TQFP44 [DX3046]
ZPSD312RL@TQFP44 [DX3046]
ZPSD312RV@TQFP44 [DX3046]
ZPSD312V@TQFP44 [DX3046]
ZPSD313@TQFP44 [DX3003]
ZPSD313L@TQFP44 [DX3003]
ZPSD313R@TQFP44 [DX3003]
ZPSD313RL@TQFP44 [DX3003]

ZPSD313RV@PLCC44 [DX2044]
ZPSD313V@PLCC44 [DX2044]
ZPSD813F2@PLCC52 [DX2052]
ZPSD313RV@TQFP44 [DX3003]
ZPSD313V@TQFP44 [DX3003]
ZPSD813F4@PLCC52 [DX2052]

XELTEK

E(E)PROM/FRAM/NVRAM

S29GL064N90TFI03 [DX1004]

PLD

XEL5128@PLCC68 [DX2068]
XEL5128A@PLCC68 [DX2068]

MICROCONTROLLER

####################11111111111TST
####################33333333333MCU
####################99999999999999
MC9S08SG16CTG [DX1092-6]
MC9S08SG16CTJ [DX1067-6]
MC9S08SG16MTG [DX1092-6]
MC9S08SG16MTJ [DX1067-6]
MC9S08SG16VTG [DX1092-6]
MC9S08SG16VTJ [DX1067-6]
MC9S08SG32CTG [DX1092-6]
MC9S08SG32CTJ [DX1067-6]
MC9S08SG32MTG [DX1092-6]
MC9S08SG32MTJ [DX1067-6]
MC9S08SG32VTG [DX1092-6]
MC9S08SG32VTJ [DX1067-6]
MC9S08SG4CTG [DX1092-6]
MC9S08SG4CTJ [DX1067-6]
MC9S08SG4MTG [DX1092-6]
MC9S08SG4MTJ [DX1067-6]
MC9S08SG4VTG [DX1092-6]
MC9S08SG4VTJ [DX1067-6]
MC9S08SG8CTG [DX1092-6]
MC9S08SG8CTJ [DX1067-6]
MC9S08SG8MTG [DX1092-6]
MC9S08SG8MTJ [DX1067-6]
MC9S08SG8VTG [DX1092-6]
MC9S08SG8VTJ [DX1067-6]
MC9S08SH4CTG [DX1092-6]
MC9S08SH4CTJ [DX1067-6]
MC9S08SH4MTG [DX1092-6]
####################222222222222UP
####################44444444444ADT
AE761K [DX3035]
MC9S08SG16CTGE [DX1092-6]
MC9S08SG16CTJE [DX1067-6]
MC9S08SG16MTGE [DX1092-6]
MC9S08SG16MTJE [DX1067-6]
MC9S08SG16VTGE [DX1092-6]
MC9S08SG16VTJE [DX1067-6]
MC9S08SG32CTGE [DX1092-6]
MC9S08SG32CTJE [DX1067-6]
MC9S08SG32MTGE [DX1092-6]
MC9S08SG32MTJE [DX1067-6]
MC9S08SG32VTGE [DX1092-6]
MC9S08SG32VTJE [DX1067-6]
MC9S08SG4CTGE [DX1092-6]
MC9S08SG4CTJE [DX1067-6]
MC9S08SG4MTGE [DX1092-6]
MC9S08SG4MTJE [DX1067-6]
MC9S08SG4VTGE [DX1092-6]
MC9S08SG4VTJE [DX1067-6]
MC9S08SG8CTGE [DX1092-6]
MC9S08SG8CTJE [DX1067-6]
MC9S08SG8MTGE [DX1092-6]
MC9S08SG8MTJE [DX1067-6]
MC9S08SG8VTGE [DX1092-6]
MC9S08SG8VTJE [DX1067-6]
MC9S08SH4CTGE [DX1092-6]
MC9S08SH4CTJE [DX1067-6]
MC9S08SH4MTGE [DX1092-6]

MC9S08SH4MTJ [DX1067-6]
MC9S08SH4MTJE [DX1067-6]
MC9S08SH4VTG [DX1092-6]
MC9S08SH4VTGE [DX1092-6]
MC9S08SH4VTJ [DX1067-6]
MC9S08SH4VTJE [DX1067-6]
MC9S08SH8CTG [DX1092-6]
MC9S08SH8CTGE [DX1092-6]
MC9S08SH8CTJ [DX1067-6]
MC9S08SH8CTJE [DX1067-6]
MC9S08SH8MTG [DX1092-6]
MC9S08SH8MTGE [DX1092-6]
MC9S08SH8MTJ [DX1067-6]
MC9S08SH8MTJE [DX1067-6]
MC9S08SH8VTG [DX1092-6]
MC9S08SH8VTGE [DX1092-6]
MC9S08SH8VTJ [DX1067-6]
MC9S08SH8VTJE [DX1067-6]
MK68F15P [DX0001]
MK68F15S@SOP18 [DX1031]
MK68F15X@SSOP20 [DX1024]
MK68F30K [DX0001]
MK68F30S@SOP28 [DX1033]
MK68F30X@SSOP28 [DX1026]
MN101EF32D(L)@QFP64 [DX3013]
MN101EF32D(L)@QFP64(parallel) [DX3013]
SP30 [DX0001]
SP5KTEST-LOG
ST7FLI49MK1B6 [DX0032]
ST7FLI49MK1T6 [DX3001]
ST7FLITE49 [DX0032]
ST7FLITE49@QFP32 [DX3001]
SYSTEM-CLK-TEST [DX0001]

XICOR

E(E)PROM/FRAM/NVRAM

X2004 [DX0001]
X2004@PLCC32 [DX2032]
X2004D [DX0001]
X2004D@PLCC32 [DX2032]
X2004I [DX0001]
X2004I@PLCC32 [DX2032]
X2210 [DX0001]
X2210@SOIC16 [DX1033]
X2210A [DX0001]
X2210A@SOIC16 [DX1033]
X2210I [DX0001]
X2210I@SOIC16 [DX1033]
X2212 [DX0001]
X2212@SOIC20 [DX1033]
X2212A [DX0001]
X2212A@SOIC20 [DX1033]
X2212I [DX0001]
X2212I@SOIC20 [DX1033]
X22C10 [DX0001]
X22C10@SOIC16 [DX1033]
X22C10I [DX0001]
X22C10I@SOIC16 [DX1033]
X22C12 [DX0001]
X22C12@SOIC20 [DX1033]
X22C12I [DX0001]
X22C12I@SOIC20 [DX1033]
X24012 [DX0001]
X24012@SOIC8 [DX1045]
X24022 [DX0001]
X24022@SOIC8 [DX1045]
X24026 [DX0001]
X24026@SOIC8 [DX1045]
X24042 [DX0001]
X24042@SOIC8 [DX1045]
X24164 [DX0001]
X24164@SOIC8 [DX1045]
X24165 [DX0001]
X24165@SOIC8 [DX1045]
X24325 [DX0001]
X24325@SOIC8 [DX1045]
X2444 [DX0001]
X2444I [DX0001]
X24645 [DX0001]
X24645@SOIC8 [DX1045]
X24C00 [DX0001]
X24C00@MSOP8 [DX1059]
X24C00@SOIC8 [DX1045]
X24C01 [DX0001]

X24C01@MSOP8 [DX1015]
X24C01@SOIC8 [DX1045]
X24C01A [DX0001]
X24C01A@SOIC8 [DX1045]
X24C01I [DX0001]
X24C01I@SOIC8 [DX1045]
X24C02 [DX0001]
X24C02@SOIC8 [DX1045]
X24C02I [DX0001]
X24C02I@SOIC8 [DX1045]
X24C04 [DX0001]
X24C04@SOIC14 [DX1030]
X24C04@SOIC8 [DX1045]
X24C04I [DX0001]
X24C04I@SOIC14 [DX1030]
X24C04I@SOIC8 [DX1045]
X24C08 [DX0001]
X24C08@SOIC14 [DX1030]
X24C08@SOIC8 [DX1045]
X24C08I [DX0001]
X24C08I@SOIC14 [DX1030]
X24C08I@SOIC8 [DX1045]
X24C16 [DX0001]
X24C16@SOIC14 [DX1030]
X24C16@SOIC8 [DX1045]
X24C16I [DX0001]
X24C16I@SOIC14 [DX1030]
X24C16I@SOIC8 [DX1045]
X24C44 [DX0001]
X24C44@SOIC8 [DX1045]
X24C44I [DX0001]
X24C44I@SOIC8 [DX1045]
X24C45 [DX0001]
X24C45@SOIC8 [DX1045]
X24C45I [DX0001]
X24C45I@SOIC8 [DX1045]
X24F008(3V) [DX0001]
X24F008(3V)@SOIC8 [DX1045]
X24F008(3V)@TSSOP14 [DX1016]
X24F008(5V) [DX0001]
X24F008(5V)@SOIC8 [DX1045]
X24F008(5V)@TSSOP14 [DX1016]
X24F016(3V) [DX0001]
X24F016(3V)@SOIC8 [DX1045]
X24F016(3V)@TSSOP14 [DX1016]
X24F016(5V) [DX0001]
X24F016(5V)@SOIC8 [DX1045]
X24F016(5V)@TSSOP14 [DX1016]
X24F032(3V) [DX0001]
X24F032(3V)@SOIC8 [DX1045]
X24F032(3V)@TSSOP14 [DX1016]
X24F032(5V) [DX0001]
X24F032(5V)@SOIC8 [DX1045]
X24F032(5V)@TSSOP14 [DX1016]
X24F064(3V) [DX0001]
X24F064(3V)@SOIC8 [DX1045]
X24F064(3V)@TSSOP20 [DX1033]
X24F064(5V) [DX0001]
X24F064(5V)@SOIC8 [DX1045]
X24F064(5V)@TSSOP20 [DX1033]
X25020 [DX0001]
X25020@SOIC8 [DX1045]
X25021 [DX0001]
X25021@SOIC8 [DX1045]
X25040 [DX0001]
X25040@SOIC8 [DX1045]
X25041 [DX0001]
X25041@SOIC8 [DX1045]
X25043 [DX0001]
X25043@MSOP8 [DX1015]
X25043@SOIC8 [DX1045]
X25043@TSSOP14 [DX1000]
X25045 [DX0001]
X25045@MSOP8 [DX1015]
X25045@SOIC8 [DX1045]
X25045@TSSOP14 [DX1000]
X25057@MSOP8 [DX1015]
X25057@TSSOP8 [DX1059]
X25080 [DX0001]
X25080@SOIC8 [DX1045]
X25080@TSSOP14 [DX1000]
X25097@MSOP8 [DX1015]
X25097@SOIC8 [DX1045]
X25097@TSSOP8 [DX1059]
X25128 [DX0001]
X25128@SOIC16 [DX1016]
X25138 [DX0001]
X25138@SOIC14 [DX1016]
X25138@SOIC16 [DX1016]
X25138@SOIC8 [DX1045]
X25138@TSSOP8 [DX1059]
X25160 [DX0001]
X25160@SOIC8 [DX1045]
X25160@TSSOP14 [DX1000]
X25163 [DX0001]
X25163@SOIC8 [DX1045]

X25163@TSSOP14 [DX1000]
X25164 [DX0001]
X25164@SOIC8 [DX1045]
X25164@TSSOP14 [DX1000]
X25165 [DX0001]
X25165@SOIC8 [DX1045]
X25165@TSSOP14 [DX1000]
X25166 [DX0001]
X25166@SOIC8 [DX1045]
X25166@TSSOP14 [DX1000]
X25168 [DX0001]
X25168@SOIC8 [DX1045]
X25168@TSSOP14 [DX1000]
X25169 [DX0001]
X25169@SOIC8 [DX1045]
X25169@TSSOP14 [DX1000]
X25170@SOIC8 [DX1045]
X25256 [DX0001]
X25256@SOIC8 [DX1045]
X25256@TSSOP20 [DX1000]
X25320 [DX0001]
X25320@SOIC8 [DX1045]
X25323@SOIC8 [DX1045]
X25323@TSSOP14 [DX1000]
X25324@SOIC8 [DX1045]
X25324@TSSOP14 [DX1000]
X25325@SOIC8 [DX1045]
X25325@TSSOP14 [DX1000]
X25326@SOIC8 [DX1045]
X25328@SOIC8 [DX1045]
X25328@TSSOP14 [DX1000]
X25329@SOIC8 [DX1045]
X25329@TSSOP14 [DX1000]
X25330@SOIC8 [DX1045]
X25330@TSSOP14 [DX1000]
X25401 [DX0001]
X25401@SOIC8 [DX1045]
X25640 [DX0001]
X25640@SOIC14 [DX1016]
X25642 [DX0001]
X25642@SOIC14 [DX1016]
X25642@SOIC8 [DX1045]
X25642@TSSOP20 [DX1000]
X25643@SOIC14 [DX1016]
X25644@SOIC14 [DX1016]
X25645@SOIC14 [DX1016]
X25648@SOIC14 [DX1016]
X25649@SOIC14 [DX1016]
X25650 [DX0001]
X25650@SOIC14 [DX1016]
X25650@SOIC8 [DX1045]
X25650@TSSOP20 [DX1000]
X25C02 [DX0001]
X25C02@SOIC8 [DX1045]
X25C02@TSSOP8 [DX1059]
X25F008(3V) [DX0001]
X25F008(3V)@SOIC8 [DX1045]
X25F008(3V)@TSSOP14 [DX1016]
X25F008(3V)@TSSOP20 [DX1033]
X25F008(5V) [DX0001]
X25F008(5V)@SOIC8 [DX1045]
X25F008(5V)@TSSOP14 [DX1016]
X25F008(5V)@TSSOP20 [DX1033]
X25F016(3V) [DX0001]
X25F016(3V)@SOIC8 [DX1045]
X25F016(3V)@TSSOP14 [DX1016]
X25F016(3V)@TSSOP20 [DX1033]
X25F016(5V) [DX0001]
X25F016(5V)@SOIC8 [DX1045]
X25F016(5V)@TSSOP14 [DX1016]
X25F016(5V)@TSSOP20 [DX1033]
X25F032(3V) [DX0001]
X25F032(3V)@SOIC8 [DX1045]
X25F032(3V)@TSSOP14 [DX1016]
X25F032(3V)@TSSOP20 [DX1033]
X25F032(5V) [DX0001]
X25F032(5V)@SOIC8 [DX1045]
X25F032(5V)@TSSOP14 [DX1016]
X25F032(5V)@TSSOP20 [DX1033]
X25F047(3V) [DX0001]
X25F047(3V)@MSOP8 [DX1015]
X25F047(3V)@SOIC8 [DX1045]
X25F047(3V)@TSSOP8 [DX1000]
X25F047(5V) [DX0001]
X25F047(5V)@MSOP8 [DX1015]
X25F047(5V)@SOIC8 [DX1045]
X25F047(5V)@TSSOP8 [DX1000]
X25F064(3V) [DX0001]
X25F064(3V)@SOIC8 [DX1045]
X25F064(3V)@TSSOP14 [DX1016]
X25F064(3V)@TSSOP20 [DX1033]
X25F064(5V) [DX0001]
X25F064(5V)@SOIC8 [DX1045]
X25F064(5V)@TSSOP14 [DX1016]
X25F064(5V)@TSSOP20 [DX1033]
X25F087(3V) [DX0001]

X25F087(3V)@MSOP8 [DX1015]
X25F087(3V)@SOIC8 [DX1045]
X25F087(3V)@TSSOP8 [DX1000]
X25F087(5V) [DX0001]
X25F087(5V)@MSOP8 [DX1015]
X25F087(5V)@SOIC8 [DX1045]
X25F087(5V)@TSSOP8 [DX1000]
X25F128(3V) [DX0001]
X25F128(3V)@SOIC16 [DX1016]
X25F128(5V) [DX0001]
X25F128(5V)@SOIC16 [DX1016]
X28010 [DX0001]
X28010@PLCC32 [DX2032]
X28010@TSOP32 [DX1002]
X2804A [DX0001]
X2804A(I) [DX0001]
X2804A(MB) [DX0001]
X2816A [DX0001]
X2816A@PLCC32 [DX2032]
X2816B [DX0001]
X2816B@PLCC32 [DX2032]
X2816BI [DX0001]
X2816BI@PLCC32 [DX2032]
X2816BMB [DX0001]
X2816C [DX0001]
X2816C@PLCC32 [DX2032]
X28256 [DX0001]
X28256@PLCC32 [DX2032]
X28256I [DX0001]
X28256I@PLCC32 [DX2032]
X2864A [DX0001]
X2864A(I) [DX0001]
X2864A(I)@PLCC32 [DX2032]
X2864A(M) [DX0001]
X2864A(M)@PLCC32 [DX2032]
X2864A(MB) [DX0001]
X2864A(MB)@PLCC32 [DX2032]
X2864A(T) [DX0001]
X2864A(T)@PLCC32 [DX2032]
X2864A@PLCC32 [DX2032]
X2864B [DX0001]
X2864B(I) [DX0001]
X2864B(I)@PLCC32 [DX2032]
X2864B(M) [DX0001]
X2864B(M)@PLCC32 [DX2032]
X2864B@PLCC32 [DX2032]
X2864H [DX0001]
X2864H(I) [DX0001]
X2864H(I)@PLCC32 [DX2032]
X2864H@PLCC32 [DX2032]
X28C010 [DX0001]
X28C010@PLCC32 [DX2032]
X28C16A [DX0001]
X28C16A@PLCC32 [DX2032]
X28C16B [DX0001]
X28C16B@PLCC32 [DX2032]
X28C16C [DX0001]
X28C16C@PLCC32 [DX2032]
X28C256 [DX0001]
X28C256@PLCC32 [DX2032]
X28C256@TSOP28 [DX1024]
X28C512 [DX0001]
X28C512@PLCC32 [DX2032]
X28C512@TSOP40 [DX1006]
X28C513 [DX0001]
X28C513@PLCC32 [DX2032]
X28C64 [DX0001]
X28C64@PLCC32 [DX2032]
X28C64@SOIC28 [DX1033]
X28C64@TSOP28 [DX1024]
X28HC16 [DX0001]
X28HC16@PLCC32 [DX2032]
X28HC16@SOIC24 [DX1033]
X28HC256 [DX0001]
X28HC256@PLCC32 [DX2032]
X28HC256@SOIC28 [DX1033]
X28HC256@TSOP28 [DX1024]
X28HC64 [DX0001]
X28HC64@PLCC32 [DX2032]
X28HC64@SOIC28 [DX1033]
X28HC64@TSOP28 [DX1024]
X28LC512 [DX0001]
X28LC512@PLCC32 [DX2032]
X28LC513 [DX0001]
X28LC513@PLCC32 [DX2032]
X28VC256 [DX0001]
X28VC256@PLCC32 [DX2032]
X28VC256@TSOP28 [DX1024]
X40231@SOIC16 [DX1033]
X40233@SOIC16 [DX1033]
X40235@SOIC16 [DX1033]
X40237@SOIC16 [DX1033]
X40239@SOIC16 [DX1033]
X4043 [DX0001]
X4043@MSOP8 [DX1000]
X4043@SOIC8 [DX1045]

X40430@SOIC14 [DX1033]
X40431@SOIC14 [DX1033]
X40434@SOIC14 [DX1033]
X40435@SOIC14 [DX1033]
X4045 [DX0001]
X4045@SOIC8 [DX1045]
X5043@MSOP8 [DX1015]
X5043@TSSOP14 [DX1000]
X5045@MSOP8 [DX1015]
X5045@TSSOP14 [DX1000]
X5083@SOIC8 [DX1045]
X5163 [DX0001]
X5163@TSSOP14 [DX1000]
X51638@SOIC8 [DX1045]
X5165 [DX0001]
X5165@TSSOP14 [DX1000]
X5168@SOIC8 [DX1045]
X5169 [DX0001]
X5169@TSSOP14 [DX1000]
X5323@SOIC8 [DX1045]
X5325 [DX0001]
X5325@TSSOP14 [DX1000]
X5328@SOIC8 [DX1045]
X5329 [DX0001]
X5329@TSSOP14 [DX1000]
X5643@SOIC14
X5643@TSSOP20 [DX1000]
X5645@SOIC14 [DX1016]
X5645@TSSOP20 [DX1000]
X5648@SOIC14 [DX1016]
X5649@SOIC14 [DX1016]
X68C64@SOIC24 [DX1033]
X76F041(3) [DX0001]
X76F041@SOIC8 [DX1044]
X76F101@SOIC8 [DX1045]
X76F400@TSSOP8 [DX1000]
X86C64@SOIC24 [DX1033]
X88064@SOIC24 [DX1033]
X88C64@SOIC24 [DX1033]
XD2210 [DX0001]
XM28C010 [DX0001]
XM28C040 [DX0001]
X40430@TSSOP14 [DX1000]
X40431@TSSOP14 [DX1000]
X40434@TSSOP14 [DX1000]
X40435@TSSOP14 [DX1000]
X4045@MSOP8 [DX1000]
X5043 [DX0001]
X5043@SOIC8 [DX1045]
X5045 [DX0001]
X5045@SOIC8 [DX1045]
X5083 [DX0001]
X5083@TSSOP8 [DX1000]
X5163@SOIC8 [DX1045]
X51638 [DX0001]
X51638@TSSOP14 [DX1000]
X5165@SOIC8 [DX1045]
X5168 [DX0001]
X5168@TSSOP14 [DX1000]
X5169@SOIC8 [DX1045]
X5323 [DX0001]
X5323@TSSOP14 [DX1000]
X5325@SOIC8 [DX1045]
X5328 [DX0001]
X5328@TSSOP14 [DX1000]
X5329@SOIC8 [DX1045]
X5643 [DX0001]
X5643@SOIC8 [DX1045]
X5645 [DX0001]
X5645@SOIC8 [DX1045]
X5648 [DX0001]
X5649
X68C64 [DX0001]
X76F041 [DX0001]
X76F041(3)@SOIC8 [DX1044]
X76F101 [DX0001]
X76F400@SOIC8 [DX1000]
X86C64 [DX0001]
X88064 [DX0001]
X88C64 [DX0001]
X88C75 [DX0001]
XD2210@SOIC16 [DX1033]
XM28C020 [DX0001]

XILINX

E(E)PROM/FRAM/NVRAM

XC1701 [DX0001]
XC1701@PLCC20 [DX2020]
XC1701@PLCC44 [DX2044]
XC1701@SOIC20 [DX1033]
XC1701L [DX0001]
XC1701L@PLCC20 [DX2020]
XC1701L@PLCC44 [DX2044]
XC1701L@SOIC20 [DX1033]
XC1702L@PLCC44 [DX2044]
XC1702L@TQFP44 [DX3005]
XC1704L@PLCC44 [DX2044]
XC1704L@TQFP44 [DX3005]
XC17128D [DX0001]
XC17128D@PLCC20 [DX2020]
XC17128D@SOIC8 [DX1045]
XC17128D@VOIC8 [DX1045]
XC17128E [DX0001]
XC17128E@PLCC20 [DX2020]
XC17128E@VOIC8 [DX1045]
XC17128EL [DX0001]
XC17128EL@PLCC20 [DX2020]
XC17128EL@VOIC8 [DX1045]
XC17128L [DX0001]
XC17128L@PLCC20 [DX2020]
XC17128L@SOIC8 [DX1045]
XC17128L@VOIC8 [DX1045]
XC17128X [DX0001]
XC17128X@PLCC20 [DX2020]
XC17128X@SOIC8 [DX1045]
XC17128X@VOIC8 [DX1045]
XC1718D [DX0001]
XC1718D@PLCC20 [DX2020]
XC1718D@SOIC8 [DX1045]
XC1718D@VOIC8 [DX1045]
XC1718L [DX0001]
XC1718L@PLCC20 [DX2020]
XC1718L@SOIC8 [DX1045]
XC1718L@VOIC8 [DX1045]
XC17256D [DX0001]
XC17256D@PLCC20 [DX2020]
XC17256D@SOIC8 [DX1045]
XC17256D@VOIC8 [DX1045]
XC17256E [DX0001]
XC17256E@PLCC20 [DX2020]
XC17256E@VOIC8 [DX1045]
XC17256EL [DX0001]
XC17256EL@PLCC20 [DX2020]
XC17256EL@VOIC8 [DX1045]
XC17256L [DX0001]
XC17256L@PLCC20 [DX2020]
XC17256L@SOIC8 [DX1045]
XC17256L@VOIC8 [DX1045]
XC17256X [DX0001]
XC17256X@PLCC20 [DX2020]
XC17256X@SOIC8 [DX1045]
XC17256X@VOIC8 [DX1045]
XC1736A [DX0001]
XC1736A@SOIC8 [DX1016]
XC1736D [DX0001]
XC1736D@PLCC20 [DX2020]
XC1736D@SOIC8 [DX1045]
XC1736D@VOIC8 [DX1045]
XC1736E [DX0001]
XC1736E@PLCC20 [DX2020]
XC1736E@SOIC8 [DX1045]
XC1736E@VOIC8 [DX1045]
XC17512L [DX0001]
XC17512L@PLCC20 [DX2020]
XC17512L@PLCC44 [DX2044]
XC17512L@SOIC20 [DX1033]
XC1765D [DX0001]
XC1765D@PLCC20 [DX2020]
XC1765D@SOIC8 [DX1045]
XC1765D@VOIC8 [DX1045]
XC1765E [DX0001]
XC1765E@PLCC20 [DX2020]
XC1765E@SOIC8 [DX1045]
XC1765E@VOIC8 [DX1045]
XC1765EL [DX0001]
XC1765EL@PLCC20 [DX2020]
XC1765EL@SOIC8 [DX1045]
XC1765EL@VOIC8 [DX1045]
XC1765L [DX0001]
XC1765L@PLCC20 [DX2020]
XC1765L@SOIC8 [DX1045]
XC1765L@VOIC8 [DX1045]
XC1765X [DX0001]
XC1765X@PLCC20 [DX2020]
XC1765X@SOIC8 [DX1045]
XC1765X@VOIC8 [DX1045]
XC17S05 [DX0001]
XC17S05@SOIC8 [DX1045]
XC17S05XL(L) [DX0001]
XC17S05XL(L)@SOIC8 [DX1045]
XC17S10 [DX0001]
XC17S10@SOIC8 [DX1045]

XC17S100A [DX0001]
XC17S100A@SOIC20 [DX1033]
XC17S100A@SOIC8 [DX1045]
XC17S100XL(L) [DX0001]
XC17S100XL(L)@SOIC20 [DX1033]
XC17S10XL(L) [DX0001]
XC17S10XL(L)@SOIC8 [DX1045]
XC17S150A [DX0001]
XC17S150A@SOIC20 [DX1033]
XC17S150A@SOIC8 [DX1045]
XC17S150XL(L) [DX0001]
XC17S150XL(L)@SOIC20 [DX1033]
XC17S15A [DX0001]
XC17S15A@SOIC20 [DX1033]
XC17S15A@SOIC8 [DX1045]
XC17S20 [DX0001]
XC17S20@SOIC8 [DX1045]
XC17S200A [DX0001]
XC17S200A@SOIC8 [DX1045]
XC17S200A@TQFP44 [DX3005]
XC17S20XL(L) [DX0001]
XC17S20XL(L)@SOIC8 [DX1045]
XC17S30 [DX0001]
XC17S30@SOIC8 [DX1045]
XC17S300A@TQFP44 [DX3005]
XC17S30A [DX0001]
XC17S30A@SOIC20 [DX1033]
XC17S30A@SOIC8 [DX1045]
XC17S30XL(L) [DX0001]
XC17S30XL(L)@SOIC8 [DX1045]
XC17S40 [DX0001]
XC17S40@SOIC20 [DX1033]
XC17S40XL(L) [DX0001]
XC17S40XL(L)@SOIC20 [DX1033]
XC17S50A [DX0001]
XC17S50A@SOIC20 [DX1033]
XC17S50A@SOIC8 [DX1045]
XC17S50XL(L) [DX0001]
XC17S50XL(L)@SOIC20 [DX1033]
XC17V01@PLCC20 [DX2020]
XC17V01@SOIC20 [DX1033]
XC17V01@SOIC8 [DX1045]
XC17V02@PLCC20 [DX2020]
XC17V02@PLCC44 [DX2044]
XC17V02@TQFP44 [DX3005]
XC17V04@PLCC20 [DX2020]
XC17V04@PLCC44 [DX2044]
XC17V04@TQFP44 [DX3005]
XC17V08@PLCC44 [DX2044]
XC17V08@TQFP44 [DX3005]
XC17V16@PLCC44 [DX2044]
XC17V16@TQFP44 [DX3005]
XC18V01@PLCC20 [DX2020]
XC18V01@SOIC20 [DX1033]
XC18V01@TQFP44 [DX3003]
XC18V02@PLCC44 [DX2144]
XC18V02@TQFP44 [DX3003]
XC18V04@PLCC44 [DX2144]
XC18V04@TQFP44 [DX3003]
XC18V256@PLCC20 [DX2020]
XC18V256@SOIC20 [DX1033]
XC18V256@TQFP44 [DX3003]
XC18V512@PLCC20 [DX2020]
XC18V512@SOIC20 [DX1033]
XC18V512@TQFP44 [DX3003]
XCF01S(VO)@TSSOP20 [DX1000]
XCF01S(VO)@TSSOP20(ISP) [DX0001]
XCF01S(VOG)@TSSOP20 [DX1000]
XCF01S(VOG)@TSSOP20(ISP) [DX0001]
XCF02S(VO)@TSSOP20 [DX1000]
XCF02S(VO)@TSSOP20(ISP) [DX0001]
XCF02S(VOG)@TSSOP20 [DX1000]
XCF02S(VOG)@TSSOP20(ISP) [DX0001]
XCF04S(VO)@TSSOP20 [DX1000]
XCF04S(VO)@TSSOP20(ISP) [DX0001]
XCF04S(VOG)@TSSOP20 [DX1000]
XCF04S(VOG)@TSSOP20(ISP) [DX0001]
XCF08P(FS)@FBGA48 [DX5022]
XCF08P(FS)@FBGA48(ISP) [DX0001]
XCF08P(FSG)@FBGA48 [DX5022]
XCF08P(FSG)@FBGA48(ISP) [DX0001]
XCF08P(VO)@TSOP48 [DX1004]
XCF08P(VO)@TSOP48(ISP) [DX0001]
XCF08P(VOG)@TSOP48 [DX1004]
XCF08P(VOG)@TSOP48(ISP) [DX0001]
XCF16P(FS)@FBGA48 [DX5022]
XCF16P(FS)@FBGA48(ISP) [DX0001]
XCF16P(FSG)@FBGA48 [DX5022]
XCF16P(FSG)@FBGA48(ISP) [DX0001]
XCF16P(VO)@TSOP48 [DX1004]
XCF16P(VO)@TSOP48(ISP) [DX0001]

XCF16P(VOG)@TSOP48 [DX1004]
XCF16P(VOG)@TSOP48(ISP) [DX0001]
XCF32P(FS)@FBGA48 [DX5022]
XCF32P(FS)@FBGA48(ISP) [DX0001]
XCF32P(FSG)@FBGA48 [DX5022]
XCF32P(FSG)@FBGA48(ISP) [DX0001]
XCF32P(VO)@TSOP48 [DX1004]
XCF32P(VO)@TSOP48(ISP) [DX0001]
XCF32P(VOG)@TSOP48 [DX1004]
XCF32P(VOG)@TSOP48(ISP) [DX0001]

PLD

PZ3032C@PLCC44 [DX2044]
PZ3032C@TQFP44 [DX3003]
PZ3032N@PLCC44 [DX2044]
PZ3032N@TQFP44 [DX3003]
PZ5032C@PLCC44 [DX2044]
PZ5032C@TQFP44 [DX3003]
PZ5032N@PLCC44 [DX2044]
PZ5032N@TQFP44 [DX3003]
XA9536XL@CSP48 [DX5112]
XA9536XL@PLCC44 [DX2044]
XA9536XL@TQFP64 [DX3011]
XA9536XL@VQFP44 [DX3003]
XC2C128@csBGA132 [DX5069]
XC2C128@TQFP100 [DX3021]
XC2C128@TQFP144 [DX3035]
XC2C256@ftBGA256 [DX5217]
XC2C256@PQFP208 [DX3075]
XC2C256@TQFP100 [DX3021]
XC2C256@TQFP144 [DX3035]
XC2C32@CP56 [DX5102]
XC2C32@PLCC44 [DX2044]
XC2C32@VQFP44 [DX3003]
XC2C32A@CP56 [DX5102]
XC2C32A@PLCC44 [DX2044]
XC2C32A@QFG32 [DX4015]
XC2C32A@VQFP44 [DX3003]
XC2C384@ftBGA256 [DX5217]
XC2C384@TQFP144 [DX3035]
XC2C512@ftBGA256 [DX5217]
XC2C512@PQFP208 [DX3075]
XC2C64@CP56 [DX5102]
XC2C64@PLCC44 [DX2044]
XC2C64@VQFP100 [DX3021]
XC2C64@VQFP44 [DX3003]
XC2C64A@CP56 [DX5102]
XC2C64A@PLCC44 [DX2044]
XC2C64A@QFG48 [DX4021]
XC2C64A@VQFP100 [DX3021]
XC2C64A@VQFP44 [DX3003]
XC7318@PLCC44 [DX2044]
XC7318@PQFP44 [DX3003]
XC7318@VQFP44 [DX3003]
XC7336@PLCC44 [DX2044]
XC7336@PQFP44 [DX3003]
XC7336@VQFP44 [DX3003]
XC7336Q@PLCC44 [DX2044]
XC7336Q@PQFP44 [DX3003]
XC7336Q@VQFP44 [DX3003]
XC7354@PLCC44 [DX2044]
XC7354@PLCC68 [DX2068]
XC7372@PLCC68 [DX2068]
XC7372@PLCC84 [DX2084]
XC7372@PQFP100 [DX3022]
XC95108@PLCC84 [DX2084]
XC95108@PQFP100 [DX3022]
XC95108@PQFP100(*) [DX0001]
XC95108@PQFP160(*) [DX0001]
XC95108@TQFP100 [DX3021]
XC95144@PQFP100 [DX3022]
XC95144@PQFP160(*) [DX3098]
XC95144@TQFP100 [DX3021]
XC95144XL@CSP144 [DX5124]
XC95144XL@TQFP100 [DX3021]
XC95144XL@TQFP144 [DX3035]
XC95144XV@CSP144 [DX5124]
XC95144XV@TQFP100 [DX3021]
XC95144XV@TQFP144 [DX3035]
XC95216@HQFP208(*) [DX0001]
XC95216@PQFP160(*) [DX0001]
XC95288@HQFP208(*) [DX3079]
XC95288XL@PQFP208 [DX3072]
XC95288XL@TQFP144 [DX3035]
XC95288XV@TQFP144 [DX3035]
XC9536@PLCC44 [DX2044]
XC9536@TQFP44 [DX3003]
XC9536XL@CSP48 [DX5112]
XC9536XL@PLCC44 [DX2044]
XC9536XL@TQFP64 [DX3011]

XC9536XL@VQFP44 [DX3003]
XC9536XV@CSP48 [DX5112]
XC9536XV@PLCC44 [DX2044]
XC9536XV@TQFP44 [DX3003]
XC9572@PLCC44 [DX2044]
XC9572@PLCC84 [DX2084]
XC9572@PQFP100 [DX3022]
XC9572@TQFP100 [DX3021]
XC9572@TQFP44 [DX3003]
XC9572XL@CSP48 [DX5112]
XC9572XL@PLCC44 [DX2044]
XC9572XL@TQFP100 [DX3021]
XC9572XL@TQFP44 [DX3003]
XC9572XL@TQFP64 [DX3011]
XC9572XV@CSP48 [DX5112]
XC9572XV@PLCC44 [DX2044]
XC9572XV@TQFP100 [DX3021]
XC9572XV@TQFP44 [DX3003]
XCR3032A@PLCC44 [DX2044]
XCR3032A@TQFP44 [DX3003]
XCR3032C@PLCC44 [DX2044]
XCR3032C@TQFP44 [DX3003]
XCR3032N@PLCC44 [DX2044]
XCR3032N@TQFP44 [DX3003]
XCR3032XL@csBGA48 [DX5112]
XCR3032XL@PLCC44 [DX2044]
XCR3032XL@TQFP44 [DX3003]
XCR3064XL@FPGA48 [DX5112]
XCR3064XL@FPGA48(*) [DX0001]
XCR3064XL@FPGA56 [DX5102]
XCR3064XL@PLCC44 [DX2044]
XCR3064XL@TQFP100 [DX3021]
XCR3064XL@TQFP44 [DX3003]
XCR3128XL@csBGA144 [DX5124]
XCR3128XL@TQFP100 [DX3021]
XCR3128XL@TQFP144 [DX3035]
XCR3256XL@TQFP144 [DX3035]
XCR3384XL@TQFP144 [DX3035]
XCR3512XL@PQFP208 [DX3074]
XCR5032A@PLCC44 [DX2044]
XCR5032A@TQFP44 [DX3003]
XCR5032C@PLCC44 [DX2044]
XCR5032C@TQFP44 [DX3003]
XCR5032N@PLCC44 [DX2044]
XCR5032N@TQFP44 [DX3003]

XINNOVA

MICROCONTROLLER

XN89F515 [DX0001]
XN89F515@PLCC44 [DX2044]
XN89F515@TQFP44 [DX3002]
XN89L515 [DX0001]
XN89L515@PLCC44 [DX2044]
XN89L515@TQFP44 [DX3002]
XN89W517 [DX0001]
XN89W517@LQFP48 [DX3007]
XN89W517@PLCC44 [DX2044]
XN89W517@PQFP44 [DX3002]

XINYANG

MICROCONTROLLER

ATtiny44A@MLF20 [DX0001]

XUMARS

MICROCONTROLLER

HS32423SP28@SOIC28 [DX1033]
HS32423SP28@SOIC28(ISP) [DX0001]

HS32533SP28@SOIC28 [DX1033]
HS32533SP28@SOIC28(ISP) [DX0001]

YMC

E(E)PROM/FRAM/NVRAM

Y24LC01 [DX0001]
Y24LC01@SOIC8 [DX1045]
Y24LC01@TSSOP8 [DX1059]
Y24LC02 [DX0001]
Y24LC02@SOIC8 [DX1045]
Y24LC02@TSSOP8 [DX1059]
Y24LC02A [DX0001]
Y24LC02A@SOIC8 [DX1045]
Y24LC02A@TSSOP8 [DX1059]
Y24LC04 [DX0001]
Y24LC04@SOIC8 [DX1045]
Y24LC04@TSSOP8 [DX1059]
Y24LC08 [DX0001]
Y24LC08@SOIC8 [DX1045]
Y24LC08@TSSOP8 [DX1059]
Y24LC16 [DX0001]
Y24LC16@SOIC8 [DX1045]
Y24LC16@TSSOP8 [DX1059]
Y24LC32 [DX0001]
Y24LC32@SOIC8 [DX1045]
Y24LC32@TSSOP8 [DX1059]
Y24LC64 [DX0001]
Y24LC64@SOIC8 [DX1045]
Y24LC64@TSSOP8 [DX1059]
Y54LC64
Y54LC64@SOIC8 [DX1045]
Y54LC64@TSSOP8 [DX1000]
Y93LC46(16bit) [DX0001]
Y93LC46(16bit)@SOIC8 [DX1045]
Y93LC46(16bit)@TSSOP8 [DX1059]
Y93LC46-08 [DX0001]
Y93LC46-08-S8 [DX1045]
Y93LC46-08-T8 [DX1059]
Y93LC66(08bit) [DX0001]
Y93LC66(08bit)@SOIC8 [DX1045]
Y93LC66(08bit)@TSSOP8 [DX1059]
Y93LC66(16bit) [DX0001]
Y93LC66(16bit)@SOIC8 [DX1045]
Y93LC66(16bit)@TSSOP8 [DX1059]
Y93LC86(08bit) [DX0001]
Y93LC86(08bit)@SOIC8 [DX1045]
Y93LC86(08bit)@TSSOP8 [DX1059]
Y93LC86(16bit) [DX0001]
Y93LC86(16bit)@SOIC8 [DX1045]
Y93LC86(16bit)@TSSOP8 [DX1059]

YSS

E(E)PROM/FRAM/NVRAM

Y25F05@SOP8 [DX1045]
Y25F05@VQFN8 [DX4005]
Y25F10@SOP8 [DX1045]
Y25F10@VQFN8 [DX4005]

YXLDZ

E(E)PROM/FRAM/NVRAM

YXL9020F [DX1045]

ZENTEL

E(E)PROM/FRAM/NVRAM

A5U1GA31ATS@TSOP48 [DX1004-1]
A5U2GA31ATS@TSOP48 [DX1004-1]
A5U2GA31BTS@TSOP48 [DX1004-1]
A5U4GA31ATS@TSOP48 [DX1004-1]
A5U8GA31ATS@TSOP48 [DX1004-1]
A5UA31ATS@TSOP48 [DX1004-3]

ZENTEL-CUSTOMER

E(E)PROM/FRAM/NVRAM

A5U1GA31AS(ST7162)@TSOP48 [DX1004]
A5U1GA31ATS@TSOP48(DaXian) [DX1004-1]

ZETTA

E(E)PROM/FRAM/NVRAM

ZD25D16 [DX0001]
ZD25D16@SOIC8[150 mil] [DX1045#1]
ZD25D16@SOIC8[200 mil] [DX1044#1]
ZD25D16@TSSOP8 [DX1000#1]
ZD25D16@WSON8 [DX4005#1]
ZD25D20@SOIC8[150 mil] [DX1045#1]
ZD25D20@SOIC8[200 mil] [DX1044#1]
ZD25D20@TSSOP8 [DX1000#1]
ZD25D20@USON8 [DX4002#1]
ZD25D40@SOIC8[150 mil] [DX1045#1]
ZD25D40@SOIC8[200 mil] [DX1044#1]
ZD25D40@TSSOP8 [DX1000#1]
ZD25D40@USON8 [DX4002#1]
ZD25D80@SOIC8[150 mil] [DX1045#1]
ZD25D80@SOIC8[200 mil] [DX1044#1]
ZD25D80@USON8 [DX4002#1]
ZD25D80@WSON8 [DX4005#1]

ZHENGXIN

E(E)PROM/FRAM/NVRAM

LX24C01 [DX0001]
LX24C01@SOIC8 [DX1045]
LX24C01@TSSOP8 [DX1059]
LX24C02 [DX0001]
LX24C02@SOIC8 [DX1045]
LX24C02@TSSOP8 [DX1059]
LX24C04 [DX0001]
LX24C04@SOIC8 [DX1045]
LX24C04@TSSOP8 [DX1059]
LX24C08 [DX0001]
LX24C08@SOIC8 [DX1045]
LX24C08@TSSOP8 [DX1059]
LX24C16 [DX0001]
LX24C16@SOIC8 [DX1045]
LX24C16@TSSOP8 [DX1059]

ZHIXIN

E(E)PROM/FRAM/NVRAM

AT45DSP041D@SOIC8 [DX1031-1]

MICROCONTROLLER

ADP1053@LFCSP40 [DX4017]

ZILOG

MICROCONTROLLER

HZN8275E@LQFP48 [DX3007]
S3F80P5@QFN24 [DX4012]
S3F80PB@QFN32 [DX4015]
S3F80PB@QFP44 [DX3046]
S3F80Q5@QFN24 [DX4012]
S3F80QB@QFP44 [DX3046]
S3F8235@QFP64 [DX3011]
S3F8274@QFP48 [DX3007]
S3F8275@QFP64 [DX3011]
S3F8285@QFP80 [DX3016]
S3F84B8@SOP20 [DX1033]
S3F84I8@SDIP42 [DX0042]
S3F84I9@SDIP42 [DX0042]
S3F84K4@DIP20
S3F84K4@SOP20 [DX1033]
S3F84NB@PQFP64 [DX3015]
S3F84P4
S3F84U8@QFP44 [DX3046]
S3F84UA@QFP44 [DX3046]
S3F84VB@PQFP64 [DX3015]
S3F8S15@LQFP48 [DX3007]
S3F8S18@LQFP48 [DX3007]
S3F8S19@LQFP48 [DX3007]
S3F8S24@DIP20
S3F8S24@SOP20 [DX1033]
S3F8S24@SSOP20 [DX1001]
S3F8S28@DIP24
S3F8S28@SOP24 [DX1033]
S3F8S34@SDIP32 [DX0032]
S3F8S35@SDIP32 [DX0032]
S3F8S38@SDIP32 [DX0032]
S3F8S39@SDIP32 [DX0032]
S3F8S45@QFP44 [DX3046]
S3F8S45@SDIP42 [DX0042]
S3F441FX@QFP64 [DX3011]
S3F80P5@SOP24 [DX1033]
S3F80PB@QFN44 [DX4018]
S3F80PB@SOP32 [DX1035]
S3F80QB@QFN44 [DX4018]
S3F8235@PQFP64 [DX3015]
S3F8235@SDIP64 [DX0064]
S3F8275@PQFP64 [DX3015]
S3F8285@PQFP80 [DX3019]
S3F84B8@DIP20
S3F84I8@QFP44 [DX3046]
S3F84I9@QFP44 [DX3046]
S3F84K4@DIP16
S3F84K4@SOP16 [DX1033]
S3F84K4@SSOP20 [DX1000]
S3F84NB@SDIP64 [DX0064]
S3F84P4@SOP8 [DX1030]
S3F84U8@SDIP42 [DX0042]
S3F84UA@SDIP42 [DX0042]
S3F84VB@SDIP64 [DX0064]
S3F8S15@QFP48 [DX3123]
S3F8S18@QFP48 [DX3123]
S3F8S19@QFP48 [DX3123]
S3F8S24@DIP24
S3F8S24@SOP24 [DX1033]
S3F8S28@DIP20
S3F8S28@SOP20 [DX1033]
S3F8S28@SSOP20 [DX1001]
S3F8S34@SOP32 [DX1035]
S3F8S35@SOP32 [DX1035]
S3F8S38@SOP32 [DX1035]
S3F8S39@SOP32 [DX1035]
S3F8S45@SDIP32 [DX0032]
S3F8S5A@QFP44 [DX3046]

S3F8S5A@SDIP42 [DX0042]
S3F8S6B@PQFP64 [DX3015]
S3F8S6B@QFP64 [DX3011]
S3F8S6B@SDIP64 [DX0064]
S3F8S7B@PQFP80 [DX3019]
S3F8S7B@QFP80 [DX3016]
S3F8S8B@PQFP100 [DX3022]
S3F8S8B@QFP100 [DX3021]
S3F9444
S3F9444@SOP8 [DX1030]
S3F9454@DIP16
S3F9454@DIP20
S3F9454@SOP20 [DX1033]
S3F9454@SSOP20 [DX1001]
S3F9488@QFP44 [DX3046]
S3F9488@SDIP32 [DX0032]
S3F9488@SDIP42 [DX0042]
S3F9488@SOP32 [DX1035]
S3F9498@SDIP30 [DX0032]
S3F9498@SDIP32 [DX0032]
S3F9498@SOP28 [DX1033]
S3F9498@SOP32 [DX1035]
S3F94A5@QFP44 [DX3046]
S3F94A5@SDIP32 [DX0032]
S3F94A5@SDIP42 [DX0042]
S3F94C4@DIP20
S3F94C4@SOP20 [DX1033]
S3F94C8@DIP20
S3F94C8@SOP20 [DX1033]
S3FC40D@QFP128 [DX3033]
Z16F2810AG20AG@LQFP64 [DX3011]
Z16F2810AG20EG@LQFP64 [DX3011]
Z16F2810AG20SG@LQFP64 [DX3011]
Z16F2810FI20AG@QFP80 [DX3019]
Z16F2810FI20EG@QFP80 [DX3019]
Z16F2810FI20SG@QFP80 [DX3019]
Z16F2810VH20AG@PLCC68 [DX2068]
Z16F2810VH20EG@PLCC68 [DX2068]
Z16F2810VH20SG@PLCC68 [DX2068]
Z16F2811AL20AG@LQFP100 [DX3043]
Z16F2811AL20EG@LQFP100 [DX3043]
Z16F2811AL20SG@LQFP100 [DX3043]
Z16F2811FI20AG@QFP80 [DX3019]
Z16F2811FI20EG@QFP80 [DX3019]
Z16F2811FI20SG@QFP80 [DX3019]
Z16F3211AL20AG@LQFP100 [DX3043]
Z16F3211AL20EG@LQFP100 [DX3043]
Z16F3211AL20SG@LQFP100 [DX3043]
Z16F3211FI20AG@QFP80 [DX3019]
Z16F3211FI20EG@QFP80 [DX3019]
Z16F3211FI20SG@QFP80 [DX3019]
Z16F6411AL20AG@LQFP100 [DX3043]
Z16F6411AL20EG@LQFP100 [DX3043]
Z16F6411AL20SG@LQFP100 [DX3043]
Z16F6411FI20AG@QFP80 [DX3019]
Z16F6411FI20EG@QFP80 [DX3019]
Z16F6411FI20SG@QFP80 [DX3019]
Z16FMC28AG20EG [DX3011]
Z16FMC28AG20SG [DX3011]
Z16FMC32AG20EG [DX3011]
Z16FMC32AG20SG [DX3011]
Z16FMC64AG20EG [DX3011]
Z16FMC64AG20SG [DX3011]
Z51F3220FNX [DX3002]
Z51F3220SKX [DX1034]
Z86733 [DX0001]
Z86733@PLCC28 [DX2028]
Z86733@SOIC28 [DX1033]
Z8673312PSC [DX0001]
Z8673312PSG [DX0001]
Z8673312SSC [DX1033]
Z8673312SSG [DX1033]
Z8673312VSC [DX2028]
Z8673312VSG [DX2028]
Z86743 [DX0001]
Z86743@PLCC44 [DX2044]
Z8674312FSC [DX3005]
Z8674312FSG [DX3005]
Z8674312PSC [DX0001]
Z8674312PSG [DX0001]
Z8674312VSC [DX2044]
Z8674312VSG [DX2044]
Z86C0208PEC [DX0001]
Z86C0208PSC [DX0001]
Z86C0208SEC@SOIC18 [DX1033]
Z86C0208SSC@SOIC18 [DX1033]
Z86D7308FSC@QFP44 [DX3002]
Z86D7308HSC@SSOP48 [DX1028]
Z86D7308PSC [DX0001]
Z86D7308VSC@PLCC44 [DX2044]
Z86D8608PSC [DX0001]
Z86D8608SSC@SOIC28 [DX1033]
Z86D8608SSG@SOIC28 [DX1033]
Z86D93@PLCC68 [DX0001]
Z86D9808PSC [DX0001]
Z86D9808SSC@SOIC28 [DX1033]

Z86D9808SSG@SOIC28 [DX1033]
Z86E02@SOIC18 [DX1033]
Z86E0208PEG [DX0001]
Z86E0208PSG [DX0001]
Z86E0208SEG [DX1033]
Z86E0208SSG [DX1033]
Z86E03@SOIC18 [DX1033]
Z86E0308PEG [DX0001]
Z86E0308PSG [DX0001]
Z86E0308SEG [DX1033]
Z86E0308SSG [DX1033]
Z86E04@SOIC18 [DX1033]
Z86E0412PEC1903 [DX0001]
Z86E0412PEG [DX0001]
Z86E0412PSC1903 [DX0001]
Z86E0412PSG [DX0001]
Z86E0412SEC1903 [DX1033]
Z86E0412SEG [DX1033]
Z86E0412SSC1903 [DX1033]
Z86E0412SSG [DX1033]
Z86E06@SOIC18 [DX1033]
Z86E07@SOIC18 [DX1033]
Z86E08@SOIC18 [DX1033]
Z86E0812PEC1903 [DX0001]
Z86E0812PEG [DX0001]
Z86E0812PSC1903 [DX0001]
Z86E0812PSG [DX0001]
Z86E0812SEC1903 [DX1033]
Z86E0812SEG [DX1033]
Z86E0812SSC1903 [DX1033]
Z86E0812SSG [DX1033]
Z86E122@SOIC20 [DX1033]
Z86E123@SOIC20 [DX1033]
Z86E124@SOIC20 [DX1033]
Z86E125@SOIC20 [DX1033]
Z86E126@SOIC20 [DX1033]
Z86E132@SOIC28 [DX1033]
Z86E133@SOIC28 [DX1033]
Z86E134@SOIC28 [DX1033]
Z86E135@SOIC28 [DX1033]
Z86E136@SOIC28 [DX1033]
Z86E142@TQFP44 [DX3005]
Z86E143@TQFP44 [DX3005]
Z86E144@TQFP44 [DX3005]
Z86E145@TQFP44 [DX3005]
Z86E146@TQFP44 [DX3005]
Z86E21 [DX0001]
Z86E21@TQFP44 [DX3005]
Z86E02 [DX0001]
Z86E0208PEC [DX0001]
Z86E0208PSC [DX0001]
Z86E0208SEC [DX1033]
Z86E0208SSC [DX1033]
Z86E03 [DX0001]
Z86E0308PEC [DX0001]
Z86E0308PSC [DX0001]
Z86E0308SEC [DX1033]
Z86E0308SSC [DX1033]
Z86E04 [DX0001]
Z86E0412PEC [DX0001]
Z86E0412PEC2004 [DX0001]
Z86E0412PSC1866 [DX0001]
Z86E0412PSC2004 [DX0001]
Z86E0412SEC [DX1033]
Z86E0412SEC2004 [DX1033]
Z86E0412SSC1866 [DX1033]
Z86E0412SSC2004 [DX1033]
Z86E06 [DX0001]
Z86E07 [DX0001]
Z86E08 [DX0001]
Z86E0812PEC [DX0001]
Z86E0812PEC2004 [DX0001]
Z86E0812PSC1866 [DX0001]
Z86E0812PSC2004 [DX0001]
Z86E0812SEC [DX1033]
Z86E0812SEC2004 [DX1033]
Z86E0812SSC1866 [DX1033]
Z86E0812SSC2004 [DX1033]
Z86E122 [DX0001]
Z86E123 [DX0001]
Z86E124 [DX0001]
Z86E125 [DX0001]
Z86E126 [DX0001]
Z86E132 [DX0001]
Z86E133 [DX0001]
Z86E134 [DX0001]
Z86E135 [DX0001]
Z86E136 [DX0001]
Z86E142 [DX0001]
Z86E143 [DX0001]
Z86E144 [DX0001]
Z86E145 [DX0001]
Z86E146 [DX0001]
Z86E15 [DX0001]
Z86E21@PLCC44 [DX2044]
Z86E2112 [DX0001]

Z86E2112@PLCC44 [DX2044]
Z86E2112@TQFP44 [DX3005]
Z86E2116 [DX0001]
Z86E2116@PLCC44 [DX2044]
Z86E2116@TQFP44 [DX3005]
Z86E23 [DX0001]
Z86E23@PLCC44 [DX2044]
Z86E23@TQFP44 [DX3005]
Z86E2312 [DX0001]
Z86E2312@PLCC44 [DX2044]
Z86E2312@TQFP44 [DX3005]
Z86E2316 [DX0001]
Z86E2316@PLCC44 [DX2044]
Z86E2316@TQFP44 [DX3005]
Z86E3016PEC [DX0001]
Z86E3016PEG [DX0001]
Z86E3016PSC [DX0001]
Z86E3016PSG [DX0001]
Z86E3016SEC@SOIC28 [DX1033]
Z86E3016SEG [DX1033]
Z86E3016SSC@SOIC28 [DX1033]
Z86E3016SSG [DX1033]
Z86E3016VEC@PLCC28 [DX2028]
Z86E3016VEG [DX2028]
Z86E3016VSC@PLCC28 [DX2028]
Z86E3016VSG@PLCC28 [DX2028]
Z86E3116PEC [DX0001]
Z86E3116PEG [DX0001]
Z86E3116PSC [DX0001]
Z86E3116PSG [DX0001]
Z86E3116SEC@SOIC28 [DX1033]
Z86E3116SEG [DX1033]
Z86E3116SSC@SOIC28 [DX1033]
Z86E3116SSG [DX1033]
Z86E3116VEC@PLCC28 [DX2028]
Z86E3116VEG [DX2028]
Z86E3116VSC@PLCC28 [DX2028]
Z86E3116VSG@PLCC28 [DX2028]
Z86E33 [DX0001]
Z86E33@PLCC28 [DX2028]
Z86E33@SOIC28 [DX1033]
Z86E3312PSC [DX0001]
Z86E3312PSG [DX0001]
Z86E3312SSC [DX1033]
Z86E3312SSG [DX1033]
Z86E3312VSC [DX2028]
Z86E3312VSG [DX2028]
Z86E34 [DX0001]
Z86E34@PLCC28 [DX2028]
Z86E34@SOIC28 [DX1033]
Z86E3412PSC [DX0001]
Z86E3412PSG [DX0001]
Z86E3412SSC [DX1033]
Z86E3412SSG [DX1033]
Z86E3412VSC [DX2028]
Z86E3412VSG [DX2028]
Z86E4016FEC@TQFP44 [DX3066]
Z86E4016FEG [DX3066]
Z86E4016FSC@TQFP44 [DX3066]
Z86E4016FSG [DX3066]
Z86E4016PEC [DX0001]
Z86E4016PEG [DX0001]
Z86E4016PSC [DX0001]
Z86E4016PSG [DX0001]
Z86E4016VEC@PLCC44 [DX2044]
Z86E4016VEG [DX2044]
Z86E4016VSC@PLCC44 [DX2044]
Z86E4016VSG@PLCC44 [DX2044]
Z86E43 [DX0001]
Z86E43@PLCC44 [DX2044]
Z86E43@TQFP44 [DX3005]
Z86E4312FSC [DX3005]
Z86E4312FSG [DX3005]
Z86E4312PSC [DX0001]
Z86E4312PSG [DX0001]
Z86E4312VSC [DX2044]
Z86E4312VSG [DX2044]
Z86E44 [DX0001]
Z86E44@PLCC44 [DX2044]
Z86E44@TQFP44 [DX3005]
Z86E4412FSC [DX3005]
Z86E4412FSG [DX3005]
Z86E4412PSC [DX0001]
Z86E4412PSG [DX0001]
Z86E4412VSC [DX2044]
Z86E4412VSG [DX2044]
Z86E6116ASC [DX3005]
Z86E6116ASG@TQFP44 [DX3005]
Z86E6116PSC [DX0001]
Z86E6116PSG [DX0001]
Z86E6116VSC@PLCC44 [DX2044]
Z86E6116VSG [DX2044]
Z86E6120ASC [DX3005]
Z86E6120ASG@TQFP44 [DX3005]
Z86E6120PSC [DX0001]
Z86E6120PSG [DX0001]

Z86E6120VSC@PLCC44 [DX2044]
Z86E6120VSG [DX2044]
Z86E61FSC@TQFP44 [DX3005]
Z86E61FSG [DX3005]
Z86E61PSC [DX0001]
Z86E61PSG [DX0001]
Z86E61VSC@PLCC44 [DX2044]
Z86E61VSG [DX2044]
Z86E6316ASC [DX3005]
Z86E6316ASG@TQFP44 [DX3005]
Z86E6316PSC [DX0001]
Z86E6316PSG [DX0001]
Z86E6316VSC@PLCC44 [DX2044]
Z86E6316VSG [DX2044]
Z86E6320ASC [DX3005]
Z86E6320ASG@TQFP44 [DX3005]
Z86E6320PSC [DX0001]
Z86E6320PSG [DX0001]
Z86E6320VSC@PLCC44 [DX2044]
Z86E6320VSG [DX2044]
Z86E63FSC@TQFP44 [DX3005]
Z86E63FSG [DX3005]
Z86E63PSC [DX0001]
Z86E63PSG [DX0001]
Z86E63VSC@PLCC44 [DX2044]
Z86E63VSG [DX2044]
Z86E72 [DX0001]
Z86E72@PLCC44 [DX2044]
Z86E72@TQFP44 [DX3005]
Z86E7216 [DX0001]
Z86E7216@PLCC44 [DX2044]
Z86E7216@TQFP44 [DX3005]
Z86E73 [DX0001]
Z86E73@PLCC44 [DX2044]
Z86E73@TQFP44 [DX3005]
Z86E7316 [DX0001]
Z86E7316@PLCC44 [DX2044]
Z86E7316@TQFP44 [DX3005]
Z86E83 [DX0001]
Z86E83@PLCC28 [DX2028]
Z86E83@SOIC28 [DX1033]
Z86E8316 [DX0001]
Z86E8316@PLCC28 [DX2028]
Z86E8316@SOIC28 [DX1033]
Z86L0208PEC [DX0001]
Z86L0208PSC [DX0001]
Z86L0208SEC@SOIC18 [DX1033]
Z86L0208SSC@SOIC18 [DX1033]
Z89371 [DX0001]
Z89371@PLCC44 [DX2044]
Z89371@TQFP44 [DX3005]
Z89371B [DX0001]
Z89371B@PLCC44 [DX2044]
Z89371B@TQFP44 [DX3005]
Z8E00010HEC@SSOP20 [DX1001]
Z8E00010HSC@SSOP20 [DX1001]
Z8E00010PEC [DX0001]
Z8E00010PSC [DX0001]
Z8E00010SEC@SOIC18 [DX1033]
Z8E00010SSC@SOIC18 [DX1033]
Z8E00010SSG@SOIC18 [DX1033]
Z8E00110HEC@SSOP20 [DX1001]
Z8E00110HSC@SSOP20 [DX1001]
Z8E00110PEC [DX0001]
Z8E00110PSC [DX0001]
Z8E00110SEC@SOIC18 [DX1033]
Z8E00110SSC@SOIC18 [DX1033]
Z8E00110SSG@SOIC18 [DX1033]
Z8F0113HH005EC@SSOP20 [DX1026]
Z8F0113HH005EG@SSOP20 [DX1026]
Z8F0113HH005SC@SSOP20 [DX1026]
Z8F0113HH005SG@SSOP20 [DX1026]
Z8F0113HJ005EC@SSOP28 [DX1026]
Z8F0113HJ005EG@SSOP28 [DX1026]
Z8F0113HJ005SC@SSOP28 [DX1026]
Z8F0113HJ005SG@SSOP28 [DX1026]
Z8F0113PB005EC [DX0001]
Z8F0113PB005EG [DX0001]
Z8F0113PB005SC [DX0001]
Z8F0113PB005SG [DX0001]
Z8F0113PH005EC [DX0001]
Z8F0113PH005EG [DX0001]
Z8F0113PH005SC [DX0001]
Z8F0113PH005SG [DX0001]
Z8F0113PJ005EC [DX0001]
Z8F0113PJ005EG [DX0001]
Z8F0113PJ005SC [DX0001]
Z8F0113PJ005SG [DX0001]
Z8F0113QB005EC@QFN8 [DX4005]
Z8F0113QB005EG@QFN8 [DX4005]
Z8F0113QB005SC@QFN8 [DX4005]
Z8F0113QB005SG@QFN8 [DX4005]
Z8F0113SB005EC@SOIC8 [DX1045]
Z8F0113SB005EG@SOIC8 [DX1045]
Z8F0113SB005SC@SOIC8 [DX1045]
Z8F0113SB005SG@SOIC8 [DX1045]

Z8F0113SH005EC@SOIC20 [DX1033]
Z8F0113SH005SC@SOIC20 [DX1033]
Z8F0113SJ005EC@SOIC28 [DX1033]
Z8F0113SJ005SC@SOIC28 [DX1033]
Z8F011AHH020EC@SSOP20 [DX1026]
Z8F011AHH020SC@SSOP20 [DX1026]
Z8F011AHJ020EC@SSOP28 [DX1026]
Z8F011AHJ020SC@SSOP28 [DX1026]
Z8F011APB020EC [DX0001]
Z8F011APB020SC [DX0001]
Z8F011APH020EC [DX0001]
Z8F011APH020SC [DX0001]
Z8F011APJ020EC [DX0001]
Z8F011APJ020SC [DX0001]
Z8F011AQB020EC@QFN8 [DX4005]
Z8F011AQB020SC@QFN8 [DX4005]
Z8F011ASB020EC@SOIC8 [DX1045]
Z8F011ASB020SC@SOIC8 [DX1045]
Z8F011ASH020EC@SOIC20 [DX1033]
Z8F011ASH020SC@SOIC20 [DX1033]
Z8F011ASJ020EC@SOIC28 [DX1033]
Z8F011ASJ020SC@SOIC28 [DX1033]
Z8F0123HH005EC@SSOP20 [DX1026]
Z8F0123HH005SC@SSOP20 [DX1026]
Z8F0123HJ005EC@SSOP28 [DX1026]
Z8F0123HJ005SC@SSOP28 [DX1026]
Z8F0123PB005EC [DX0001]
Z8F0123PB005SC [DX0001]
Z8F0123PH005EC [DX0001]
Z8F0123PH005SC [DX0001]
Z8F0123PJ005EC [DX0001]
Z8F0123PJ005SC [DX0001]
Z8F0123QB005EC@QFN8 [DX4005]
Z8F0123QB005SC@QFN8 [DX4005]
Z8F0123SB005EC@SOIC8 [DX1045]
Z8F0123SB005SC@SOIC8 [DX1045]
Z8F0123SH005EC@SOIC20 [DX1033]
Z8F0123SH005SC@SOIC20 [DX1033]
Z8F0123SJ005EC@SOIC28 [DX1033]
Z8F0123SJ005SC@SOIC28 [DX1033]
Z8F012AHH020EC@SSOP20 [DX1026]
Z8F012AHH020SC@SSOP20 [DX1026]
Z8F012AHJ020EC@SSOP28 [DX1026]
Z8F012AHJ020SC@SSOP28 [DX1026]
Z8F012APB020EC [DX0001]
Z8F012APB020SC [DX0001]
Z8F012APH020EC [DX0001]
Z8F012APH020SC [DX0001]
Z8F0113SH005EG@SOIC20 [DX1033]
Z8F0113SH005SG@SOIC20 [DX1033]
Z8F0113SJ005EG@SOIC28 [DX1033]
Z8F0113SJ005SG@SOIC28 [DX1033]
Z8F011AHH020EG@SSOP20 [DX1026]
Z8F011AHH020SG@SSOP20 [DX1026]
Z8F011AHJ020EG@SSOP28 [DX1026]
Z8F011AHJ020SG@SSOP28 [DX1026]
Z8F011APB020EG [DX0001]
Z8F011APB020SG [DX0001]
Z8F011APH020EG [DX0001]
Z8F011APH020SG [DX0001]
Z8F011APJ020EG [DX0001]
Z8F011APJ020SG [DX0001]
Z8F011AQB020EG@QFN8 [DX4005]
Z8F011AQB020SG@QFN8 [DX4005]
Z8F011ASB020EG@SOIC8 [DX1045]
Z8F011ASB020SG@SOIC8 [DX1045]
Z8F011ASH020EG@SOIC20 [DX1033]
Z8F011ASH020SG@SOIC20 [DX1033]
Z8F011ASJ020EG@SOIC28 [DX1033]
Z8F011ASJ020SG@SOIC28 [DX1033]
Z8F0123HH005EG@SSOP20 [DX1026]
Z8F0123HH005SG@SSOP20 [DX1026]
Z8F0123HJ005EG@SSOP28 [DX1026]
Z8F0123HJ005SG@SSOP28 [DX1026]
Z8F0123PB005EG [DX0001]
Z8F0123PB005SG [DX0001]
Z8F0123PH005EG [DX0001]
Z8F0123PH005SG [DX0001]
Z8F0123PJ005EG [DX0001]
Z8F0123PJ005SG [DX0001]
Z8F0123QB005EG@QFN8 [DX4005]
Z8F0123QB005SG@QFN8 [DX4005]
Z8F0123SB005EG@SOIC8 [DX1045]
Z8F0123SB005SG@SOIC8 [DX1045]
Z8F0123SH005EG@SOIC20 [DX1033]
Z8F0123SH005SG@SOIC20 [DX1033]
Z8F0123SJ005EG@SOIC28 [DX1033]
Z8F0123SJ005SG@SOIC28 [DX1033]
Z8F012AHH020EG@SSOP20 [DX1026]
Z8F012AHH020SG@SSOP20 [DX1026]
Z8F012AHJ020EG@SSOP28 [DX1026]
Z8F012AHJ020SG@SSOP28 [DX1026]
Z8F012APB020EG [DX0001]
Z8F012APB020SG [DX0001]
Z8F012APH020EG [DX0001]
Z8F012APH020SG [DX0001]

Z8F012APJ020EC [DX0001]
Z8F012APJ020SC [DX0001]
Z8F012AQB020EC@QFN8 [DX4005]
Z8F012AQB020SC@QFN8 [DX4005]
Z8F012ASB020EC@SOIC8 [DX1045]
Z8F012ASB020SC@SOIC8 [DX1045]
Z8F012ASH020EC@SOIC20 [DX1033]
Z8F012ASH020SC@SOIC20 [DX1033]
Z8F012ASJ020EC@SOIC28 [DX1033]
Z8F012ASJ020SC@SOIC28 [DX1033]
Z8F0130HH020EG@SSOP20 [DX1026]
Z8F0130HJ020EG@SSOP28 [DX1026]
Z8F0130PH020EG [DX0001]
Z8F0130PJ020EG [DX0001]
Z8F0130QH020EG@QFN20 [DX4025]
Z8F0130QJ020EG@QFN28 [DX4013]
Z8F0130SH020EG@SOIC20 [DX1033]
Z8F0130SJ020EG@SOIC28 [DX1033]
Z8F0131HH020EG@SSOP20 [DX1026]
Z8F0131HJ020EG@SSOP28 [DX1026]
Z8F0131PH020EG [DX0001]
Z8F0131PJ020EG [DX0001]
Z8F0131QH020EG@QFN20 [DX4025]
Z8F0131QJ020EG@QFN28 [DX4013]
Z8F0131SH020EG@SOIC20 [DX1033]
Z8F0131SJ020EG@SOIC28 [DX1033]
Z8F0213HH005EC@SSOP20 [DX1026]
Z8F0213HH005SC@SSOP20 [DX1026]
Z8F0213HJ005EC@SSOP28 [DX1026]
Z8F0213HJ005SC@SSOP28 [DX1026]
Z8F0213PB005EC [DX0001]
Z8F0213PB005SC [DX0001]
Z8F0213PH005EC [DX0001]
Z8F0213PH005SC [DX0001]
Z8F0213PJ005EC [DX0001]
Z8F0213PJ005SC [DX0001]
Z8F0213QB005EC@QFN8 [DX4005]
Z8F0213QB005SC@QFN8 [DX4005]
Z8F0213SB005EC@SOIC8 [DX1045]
Z8F0213SB005SC@SOIC8 [DX1045]
Z8F0213SH005EC@SOIC20 [DX1033]
Z8F0213SH005SC@SOIC20 [DX1033]
Z8F0213SJ005EC@SOIC28 [DX1033]
Z8F0213SJ005SC@SOIC28 [DX1033]
Z8F021AHH020EC@SSOP20 [DX1026]
Z8F021AHH020SC@SSOP20 [DX1026]
Z8F021AHJ020EC@SSOP28 [DX1026]
Z8F021AHJ020SC@SSOP28 [DX1026]
Z8F012APJ020EG [DX0001]
Z8F012APJ020SG [DX0001]
Z8F012AQB020EG@QFN8 [DX4005]
Z8F012AQB020SG@QFN8 [DX4005]
Z8F012ASB020EG@SOIC8 [DX1045]
Z8F012ASB020SG@SOIC8 [DX1045]
Z8F012ASH020EG@SOIC20 [DX1033]
Z8F012ASH020SG@SOIC20 [DX1033]
Z8F012ASJ020EG@SOIC28 [DX1033]
Z8F012ASJ020SG@SOIC28 [DX1033]
Z8F0130HH020SG@SSOP20 [DX1026]
Z8F0130HJ020SG@SSOP28 [DX1026]
Z8F0130PH020SG [DX0001]
Z8F0130PJ020SG [DX0001]
Z8F0130QH020SG@QFN20 [DX4025]
Z8F0130QJ020SG@QFN28 [DX4013]
Z8F0130SH020SG@SOIC20 [DX1033]
Z8F0130SJ020SG@SOIC28 [DX1033]
Z8F0131HH020SG@SSOP20 [DX1026]
Z8F0131HJ020SG@SSOP28 [DX1026]
Z8F0131PH020SG [DX0001]
Z8F0131PJ020SG [DX0001]
Z8F0131QH020SG@QFN20 [DX4025]
Z8F0131QJ020SG@QFN28 [DX4013]
Z8F0131SH020SG@SOIC20 [DX1033]
Z8F0131SJ020SG@SOIC28 [DX1033]
Z8F0213HH005EG@SSOP20 [DX1026]
Z8F0213HH005SG@SSOP20 [DX1026]
Z8F0213HJ005EG@SSOP28 [DX1026]
Z8F0213HJ005SG@SSOP28 [DX1026]
Z8F0213PB005EG [DX0001]
Z8F0213PB005SG [DX0001]
Z8F0213PH005EG [DX0001]
Z8F0213PH005SG [DX0001]
Z8F0213PJ005EG [DX0001]
Z8F0213PJ005SG [DX0001]
Z8F0213QB005EG@QFN8 [DX4005]
Z8F0213QB005SG@QFN8 [DX4005]
Z8F0213SB005EG@SOIC8 [DX1045]
Z8F0213SB005SG@SOIC8 [DX1045]
Z8F0213SH005EG@SOIC20 [DX1033]
Z8F0213SH005SG@SOIC20 [DX1033]
Z8F0213SJ005EG@SOIC28 [DX1033]
Z8F0213SJ005SG@SOIC28 [DX1033]
Z8F021AHH020EG@SSOP20 [DX1026]
Z8F021AHH020SG@SSOP20 [DX1026]
Z8F021AHJ020EG@SSOP28 [DX1026]
Z8F021AHJ020SG@SSOP28 [DX1026]

Z8F021APB020EC [DX0001]
Z8F021APB020SC [DX0001]
Z8F021APH020EC [DX0001]
Z8F021APH020SC [DX0001]
Z8F021APJ020EC [DX0001]
Z8F021APJ020SC [DX0001]
Z8F021AQB020EC@QFN8 [DX4005]
Z8F021AQB020SC@QFN8 [DX4005]
Z8F021ASB020EC@SOIC8 [DX1045]
Z8F021ASB020SC@SOIC8 [DX1045]
Z8F021ASH020EC@SOIC20 [DX1033]
Z8F021ASH020SC@SOIC20 [DX1033]
Z8F021ASJ020EC@SOIC28 [DX1033]
Z8F021ASJ020SC@SOIC28 [DX1033]
Z8F0223HH005EC@SSOP20 [DX1026]
Z8F0223HH005SC@SSOP20 [DX1026]
Z8F0223HJ005EC@SSOP28 [DX1026]
Z8F0223HJ005SC@SSOP28 [DX1026]
Z8F0223PB005EC [DX0001]
Z8F0223PB005SC [DX0001]
Z8F0223PH005EC [DX0001]
Z8F0223PH005SC [DX0001]
Z8F0223PJ005EC [DX0001]
Z8F0223PJ005SC [DX0001]
Z8F0223QB005EC@QFN8 [DX4005]
Z8F0223QB005SC@QFN8 [DX4005]
Z8F0223SB005EC@SOIC8 [DX1045]
Z8F0223SB005SC@SOIC8 [DX1045]
Z8F0223SH005EC@SOIC20 [DX1033]
Z8F0223SH005SC@SOIC20 [DX1033]
Z8F0223SJ005EC@SOIC28 [DX1033]
Z8F0223SJ005SC@SOIC28 [DX1033]
Z8F022AHH020EC@SSOP20 [DX1026]
Z8F022AHH020SC@SSOP20 [DX1026]
Z8F022AHJ020EC@SSOP28 [DX1026]
Z8F022AHJ020SC@SSOP28 [DX1026]
Z8F022APB020EC [DX0001]
Z8F022APB020SC [DX0001]
Z8F022APH020EC [DX0001]
Z8F022APH020SC [DX0001]
Z8F022APJ020EC [DX0001]
Z8F022APJ020SC [DX0001]
Z8F022AQB020EC@QFN8 [DX4005]
Z8F022AQB020SC@QFN8 [DX4005]
Z8F022ASB020EC@SOIC8 [DX1045]
Z8F022ASB020SC@SOIC8 [DX1045]
Z8F022ASH020EC@SOIC20 [DX1033]
Z8F022ASH020SC@SOIC20 [DX1033]

Z8F021APB020EG [DX0001]
Z8F021APB020SG [DX0001]
Z8F021APH020EG [DX0001]
Z8F021APH020SG [DX0001]
Z8F021APJ020EG [DX0001]
Z8F021APJ020SG [DX0001]
Z8F021AQB020EG@QFN8 [DX4005]
Z8F021AQB020SG@QFN8 [DX4005]
Z8F021ASB020EG@SOIC8 [DX1045]
Z8F021ASB020SG@SOIC8 [DX1045]
Z8F021ASH020EG@SOIC20 [DX1033]
Z8F021ASH020SG@SOIC20 [DX1033]
Z8F021ASJ020EG@SOIC28 [DX1033]
Z8F021ASJ020SG@SOIC28 [DX1033]
Z8F0223HH005EG@SSOP20 [DX1026]
Z8F0223HH005SG@SSOP20 [DX1026]
Z8F0223HJ005EG@SSOP28 [DX1026]
Z8F0223HJ005SG@SSOP28 [DX1026]
Z8F0223PB005EG [DX0001]
Z8F0223PB005SG [DX0001]
Z8F0223PH005EG [DX0001]
Z8F0223PH005SG [DX0001]
Z8F0223PJ005EG [DX0001]
Z8F0223PJ005SG [DX0001]
Z8F0223QB005EG@QFN8 [DX4005]
Z8F0223QB005SG@QFN8 [DX4005]
Z8F0223SB005EG@SOIC8 [DX1045]
Z8F0223SB005SG@SOIC8 [DX1045]
Z8F0223SH005EG@SOIC20 [DX1033]
Z8F0223SH005SG@SOIC20 [DX1033]
Z8F0223SJ005EG@SOIC28 [DX1033]
Z8F0223SJ005SG@SOIC28 [DX1033]
Z8F022AHH020EG@SSOP20 [DX1026]
Z8F022AHH020SG@SSOP20 [DX1026]
Z8F022AHJ020EG@SSOP28 [DX1026]
Z8F022AHJ020SG@SSOP28 [DX1026]
Z8F022APB020EG [DX0001]
Z8F022APB020SG [DX0001]
Z8F022APH020EG [DX0001]
Z8F022APH020SG [DX0001]
Z8F022APJ020EG [DX0001]
Z8F022APJ020SG [DX0001]
Z8F022AQB020EG@QFN8 [DX4005]
Z8F022AQB020SG@QFN8 [DX4005]
Z8F022ASB020EG@SOIC8 [DX1045]
Z8F022ASB020SG@SOIC8 [DX1045]
Z8F022ASH020EG@SOIC20 [DX1033]
Z8F022ASH020SG@SOIC20 [DX1033]

Z8F022ASJ020EC@SOIC28 [DX1033]
Z8F022ASJ020SC@SOIC28 [DX1033]
Z8F0230HH020EG@SSOP20 [DX1026]
Z8F0230HJ020EG@SSOP28 [DX1026]
Z8F0230PH020EG [DX0001]
Z8F0230PJ020EG [DX0001]
Z8F0230QH020EG@QFN20 [DX4025]
Z8F0230QJ020EG@QFN28 [DX4013]
Z8F0230SH020EG@SOIC20 [DX1033]
Z8F0230SJ020EG@SOIC28 [DX1033]
Z8F0231HH020EG@SSOP20 [DX1026]
Z8F0231HJ020EG@SSOP28 [DX1026]
Z8F0231PH020EG [DX0001]
Z8F0231PJ020EG [DX0001]
Z8F0231QH020EG@QFN20 [DX4025]
Z8F0231QJ020EG@QFN28 [DX4013]
Z8F0231SH020EG@SOIC20 [DX1033]
Z8F0231SJ020EG@SOIC28 [DX1033]
Z8F0411HH020EC@SSOP20 [DX1026]
Z8F0411HH020SC@SSOP20 [DX1026]
Z8F0411PH020EC [DX0001]
Z8F0411PH020SC [DX0001]
Z8F0412PJ020EC [DX0001]
Z8F0412PJ020SC [DX0001]
Z8F0412SJ020EC@SOIC28 [DX1033]
Z8F0412SJ020SC@SOIC28 [DX1033]
Z8F0413HH005EC@SSOP20 [DX1026]
Z8F0413HH005SC@SSOP20 [DX1026]
Z8F0413HJ005EC@SSOP28 [DX1026]
Z8F0413HJ005SC@SSOP28 [DX1026]
Z8F0413PB005EC [DX0001]
Z8F0413PB005SC [DX0001]
Z8F0413PH005EC [DX0001]
Z8F0413PH005SC [DX0001]
Z8F0413PJ005EC [DX0001]
Z8F0413PJ005SC [DX0001]
Z8F0413QB005EC@QFN8 [DX4005]
Z8F0413QB005SC@QFN8 [DX4005]
Z8F0413SB005EC@SOIC8 [DX1045]
Z8F0413SB005SC@SOIC8 [DX1045]
Z8F0413SH005EC@SOIC20 [DX1033]
Z8F0413SH005SC@SOIC20 [DX1033]
Z8F0413SJ005EC@SOIC28 [DX1033]
Z8F0413SJ005SC@SOIC28 [DX1033]
Z8F041AHH020EC@SSOP20 [DX1026]
Z8F041AHH020SC@SSOP20 [DX1026]
Z8F041AHJ020EC@SSOP28 [DX1026]
Z8F041AHJ020SC@SSOP28 [DX1026]
Z8F022ASJ020EG@SOIC28 [DX1033]
Z8F022ASJ020SG@SOIC28 [DX1033]
Z8F0230HH020SG@SSOP20 [DX1026]
Z8F0230HJ020SG@SSOP28 [DX1026]
Z8F0230PH020SG [DX0001]
Z8F0230PJ020SG [DX0001]
Z8F0230QH020SG@QFN20 [DX4025]
Z8F0230QJ020SG@QFN28 [DX4013]
Z8F0230SH020SG@SOIC20 [DX1033]
Z8F0230SJ020SG@SOIC28 [DX1033]
Z8F0231HH020SG@SSOP20 [DX1026]
Z8F0231HJ020SG@SSOP28 [DX1026]
Z8F0231PH020SG [DX0001]
Z8F0231PJ020SG [DX0001]
Z8F0231QH020SG@QFN20 [DX4025]
Z8F0231QJ020SG@QFN28 [DX4013]
Z8F0231SH020SG@SOIC20 [DX1033]
Z8F0231SJ020SG@SOIC28 [DX1033]
Z8F0411HH020EG@SSOP20 [DX1026]
Z8F0411HH020SG@SSOP20 [DX1026]
Z8F0411PH020EG [DX0001]
Z8F0411PH020SG [DX0001]
Z8F0412PJ020EG [DX0001]
Z8F0412PJ020SG [DX0001]
Z8F0412SJ020EG@SOIC28 [DX1033]
Z8F0412SJ020SG@SOIC28 [DX1033]
Z8F0413HH005EG@SSOP20 [DX1026]
Z8F0413HH005SG@SSOP20 [DX1026]
Z8F0413HJ005EG@SSOP28 [DX1026]
Z8F0413HJ005SG@SSOP28 [DX1026]
Z8F0413PB005EG [DX0001]
Z8F0413PB005SG [DX0001]
Z8F0413PH005EG [DX0001]
Z8F0413PH005SG [DX0001]
Z8F0413PJ005EG [DX0001]
Z8F0413PJ005SG [DX0001]
Z8F0413QB005EG@QFN8 [DX4005]
Z8F0413QB005SG@QFN8 [DX4005]
Z8F0413SB005EG@SOIC8 [DX1045]
Z8F0413SB005SG@SOIC8 [DX1045]
Z8F0413SH005EG@SOIC20 [DX1033]
Z8F0413SH005SG@SOIC20 [DX1033]
Z8F0413SJ005EG@SOIC28 [DX1033]
Z8F0413SJ005SG@SOIC28 [DX1033]
Z8F041AHH020EG@SSOP20 [DX1026]
Z8F041AHH020SG@SSOP20 [DX1026]
Z8F041AHJ020EG@SSOP28 [DX1026]
Z8F041AHJ020SG@SSOP28 [DX1026]

Z8F041APB020EC [DX0001]
Z8F041APB020SC [DX0001]
Z8F041APH020EC [DX0001]
Z8F041APH020SC [DX0001]
Z8F041APJ020EC [DX0001]
Z8F041APJ020SC [DX0001]
Z8F041AQB020EC@QFN8 [DX4005]
Z8F041AQB020SC@QFN8 [DX4005]
Z8F041ASB020EC@SOIC8 [DX1045]
Z8F041ASB020SC@SOIC8 [DX1045]
Z8F041ASH020EC@SOIC20 [DX1033]
Z8F041ASH020SC@SOIC20 [DX1033]
Z8F041ASJ020EC@SOIC28 [DX1033]
Z8F041ASJ020SC@SOIC28 [DX1033]
Z8F0421HH020EC@SSOP20 [DX1026]
Z8F0421HH020SC@SSOP20 [DX1026]
Z8F0421PH020EC [DX0001]
Z8F0421PH020SC [DX0001]
Z8F0422PJ020EC [DX0001]
Z8F0422PJ020SC [DX0001]
Z8F0422SJ020EC@SOIC28 [DX1033]
Z8F0422SJ020SC@SOIC28 [DX1033]
Z8F0423HH005EC@SSOP20 [DX1026]
Z8F0423HH005SC@SSOP20 [DX1026]
Z8F0423HJ005EC@SSOP28 [DX1026]
Z8F0423HJ005SC@SSOP28 [DX1026]
Z8F0423PB005EC [DX0001]
Z8F0423PB005SC [DX0001]
Z8F0423PH005EC [DX0001]
Z8F0423PH005SC [DX0001]
Z8F0423PJ005EC [DX0001]
Z8F0423PJ005SC [DX0001]
Z8F0423QB005EC@QFN8 [DX4005]
Z8F0423QB005SC@QFN8 [DX4005]
Z8F0423SB005EC@SOIC8 [DX1045]
Z8F0423SB005SC@SOIC8 [DX1045]
Z8F0423SH005EC@SOIC20 [DX1033]
Z8F0423SH005SC@SOIC20 [DX1033]
Z8F0423SJ005EC@SOIC28 [DX1033]
Z8F0423SJ005SC@SOIC28 [DX1033]
Z8F042AHH020EC@SSOP20 [DX1026]
Z8F042AHH020SC@SSOP20 [DX1026]
Z8F042AHJ020EC@SSOP28 [DX1026]
Z8F042AHJ020SC@SSOP28 [DX1026]
Z8F042APB020EC [DX0001]
Z8F042APB020SC [DX0001]
Z8F042APH020EC [DX0001]
Z8F042APH020SC [DX0001]
Z8F041APB020EG [DX0001]
Z8F041APB020SG [DX0001]
Z8F041APH020EG [DX0001]
Z8F041APH020SG [DX0001]
Z8F041APJ020EG [DX0001]
Z8F041APJ020SG [DX0001]
Z8F041AQB020EG@QFN8 [DX4005]
Z8F041AQB020SG@QFN8 [DX4005]
Z8F041ASB020EG@SOIC8 [DX1045]
Z8F041ASB020SG@SOIC8 [DX1045]
Z8F041ASH020EG@SOIC20 [DX1033]
Z8F041ASH020SG@SOIC20 [DX1033]
Z8F041ASJ020EG@SOIC28 [DX1033]
Z8F041ASJ020SG@SOIC28 [DX1033]
Z8F0421HH020EG@SSOP20 [DX1026]
Z8F0421HH020SG@SSOP20 [DX1026]
Z8F0421PH020EG [DX0001]
Z8F0421PH020SG [DX0001]
Z8F0422PJ020EG [DX0001]
Z8F0422PJ020SG [DX0001]
Z8F0422SJ020EG@SOIC28 [DX1033]
Z8F0422SJ020SG@SOIC28 [DX1033]
Z8F0423HH005EG@SSOP20 [DX1026]
Z8F0423HH005SG@SSOP20 [DX1026]
Z8F0423HJ005EG@SSOP28 [DX1026]
Z8F0423HJ005SG@SSOP28 [DX1026]
Z8F0423PB005EG [DX0001]
Z8F0423PB005SG [DX0001]
Z8F0423PH005EG [DX0001]
Z8F0423PH005SG [DX0001]
Z8F0423PJ005EG [DX0001]
Z8F0423PJ005SG [DX0001]
Z8F0423QB005EG@QFN8 [DX4005]
Z8F0423QB005SG@QFN8 [DX4005]
Z8F0423SB005EG@SOIC8 [DX1045]
Z8F0423SB005SG@SOIC8 [DX1045]
Z8F0423SH005EG@SOIC20 [DX1033]
Z8F0423SH005SG@SOIC20 [DX1033]
Z8F0423SJ005EG@SOIC28 [DX1033]
Z8F0423SJ005SG@SOIC28 [DX1033]
Z8F042AHH020EG@SSOP20 [DX1026]
Z8F042AHH020SG@SSOP20 [DX1026]
Z8F042AHJ020EG@SSOP28 [DX1026]
Z8F042AHJ020SG@SSOP28 [DX1026]
Z8F042APB020EG [DX0001]
Z8F042APB020SG [DX0001]
Z8F042APH020EG [DX0001]
Z8F042APH020SG [DX0001]

Z8F042APJ020EC [DX0001]
Z8F042APJ020SC [DX0001]
Z8F042AQB020EC@QFN8 [DX4005]
Z8F042AQB020SC@QFN8 [DX4005]
Z8F042ASB020EC@SOIC8 [DX1045]
Z8F042ASB020SC@SOIC8 [DX1045]
Z8F042ASH020EC@SOIC20 [DX1033]
Z8F042ASH020SC@SOIC20 [DX1033]
Z8F042ASJ020EC@SOIC28 [DX1033]
Z8F042ASJ020SC@SOIC28 [DX1033]
Z8F0430HH020EG@SSOP20 [DX1026]
Z8F0430HJ020EG@SSOP28 [DX1026]
Z8F0430PH020EG [DX0001]
Z8F0430PJ020EG [DX0001]
Z8F0430QH020EG@QFN20 [DX4025]
Z8F0430QJ020EG@QFN28 [DX4013]
Z8F0430SH020EG@SOIC20 [DX1033]
Z8F0430SJ020EG@SOIC28 [DX1033]
Z8F0431HH020EG@SSOP20 [DX1026]
Z8F0431HJ020EG@SSOP28 [DX1026]
Z8F0431PH020EG [DX0001]
Z8F0431PJ020EG [DX0001]
Z8F0431QH020EG@QFN20 [DX4025]
Z8F0431QJ020EG@QFN28 [DX4013]
Z8F0431SH020EG@SOIC20 [DX1033]
Z8F0431SJ020EG@SOIC28 [DX1033]
Z8F043AHH020EG@SSOP20 [DX1026]
Z8F043AHJ020EG@SSOP28 [DX1026]
Z8F043APH020EG [DX0001]
Z8F043APJ020EG [DX0001]
Z8F043AQH020EG@QFN20 [DX4025]
Z8F043AQJ020EG@QFN28 [DX4013]
Z8F043ASH020EG@SOIC20 [DX1033]
Z8F043ASJ020EG@SOIC28 [DX1033]
Z8F0811HH020EC@SSOP20 [DX1026]
Z8F0811HH020SC@SSOP20 [DX1026]
Z8F0811PH020EC [DX0001]
Z8F0811PH020SC [DX0001]
Z8F0812PJ020EC [DX0001]
Z8F0812PJ020SC [DX0001]
Z8F0812SJ020EC@SOIC28 [DX1033]
Z8F0812SJ020SC@SOIC28 [DX1033]
Z8F0813HH005EC@SSOP20 [DX1026]
Z8F0813HH005SC@SSOP20 [DX1026]
Z8F0813HJ020EC@SSOP28 [DX1026]
Z8F0813HJ020SC@SSOP28 [DX1026]
Z8F0813PB005EC [DX0001]
Z8F0813PB005SC [DX0001]

Z8F042APJ020EG [DX0001]
Z8F042APJ020SG [DX0001]
Z8F042AQB020EG@QFN8 [DX4005]
Z8F042AQB020SG@QFN8 [DX4005]
Z8F042ASB020EG@SOIC8 [DX1045]
Z8F042ASB020SG@SOIC8 [DX1045]
Z8F042ASH020EG@SOIC20 [DX1033]
Z8F042ASH020SG@SOIC20 [DX1033]
Z8F042ASJ020EG@SOIC28 [DX1033]
Z8F042ASJ020SG@SOIC28 [DX1033]
Z8F0430HH020SG@SSOP20 [DX1026]
Z8F0430HJ020SG@SSOP28 [DX1026]
Z8F0430PH020SG [DX0001]
Z8F0430PJ020SG [DX0001]
Z8F0430QH020SG@QFN20 [DX4025]
Z8F0430QJ020SG@QFN28 [DX4013]
Z8F0430SH020SG@SOIC20 [DX1033]
Z8F0430SJ020SG@SOIC28 [DX1033]
Z8F0431HH020SG@SSOP20 [DX1026]
Z8F0431HJ020SG@SSOP28 [DX1026]
Z8F0431PH020SG [DX0001]
Z8F0431PJ020SG [DX0001]
Z8F0431QH020SG@QFN20 [DX4025]
Z8F0431QJ020SG@QFN28 [DX4013]
Z8F0431SH020SG@SOIC20 [DX1033]
Z8F0431SJ020SG@SOIC28 [DX1033]
Z8F043AHH020SG@SSOP20 [DX1026]
Z8F043AHJ020SG@SSOP28 [DX1026]
Z8F043APH020SG [DX0001]
Z8F043APJ020SG [DX0001]
Z8F043AQH020SG@QFN20 [DX4025]
Z8F043AQJ020SG@QFN28 [DX4013]
Z8F043ASH020SG@SOIC20 [DX1033]
Z8F043ASJ020SG@SOIC28 [DX1033]
Z8F0811HH020EG@SSOP20 [DX1026]
Z8F0811HH020SG@SSOP20 [DX1026]
Z8F0811PH020EG [DX0001]
Z8F0811PH020SG [DX0001]
Z8F0812PJ020EG [DX0001]
Z8F0812PJ020SG [DX0001]
Z8F0812SJ020EG@SOIC28 [DX1033]
Z8F0812SJ020SG@SOIC28 [DX1033]
Z8F0813HH005EG@SSOP20 [DX1026]
Z8F0813HH005SG@SSOP20 [DX1026]
Z8F0813HJ020EG@SSOP28 [DX1026]
Z8F0813HJ020SG@SSOP28 [DX1026]
Z8F0813PB005EG [DX0001]
Z8F0813PB005SG [DX0001]

Z8F0813PH005EC [DX0001]
Z8F0813PH005SC [DX0001]
Z8F0813PJ020EC [DX0001]
Z8F0813PJ020SC [DX0001]
Z8F0813QB005EC@QFN8 [DX4005]
Z8F0813QB005SC@QFN8 [DX4005]
Z8F0813SB005EC@SOIC8 [DX1045]
Z8F0813SB005SC@SOIC8 [DX1045]
Z8F0813SH005EC@SOIC20 [DX1033]
Z8F0813SH005SC@SOIC20 [DX1033]
Z8F0813SJ020EC@SOIC28 [DX1033]
Z8F0813SJ020SC@SOIC28 [DX1033]
Z8F081AHH005EC@SSOP20 [DX1026]
Z8F081AHH005SC@SSOP20 [DX1026]
Z8F081AHJ020EC@SSOP28 [DX1026]
Z8F081AHJ020SC@SSOP28 [DX1026]
Z8F081APB020EC [DX0001]
Z8F081APB020SC [DX0001]
Z8F081APH005EC [DX0001]
Z8F081APH005SC [DX0001]
Z8F081APJ020EC [DX0001]
Z8F081APJ020SC [DX0001]
Z8F081AQB020EC@QFN8 [DX4005]
Z8F081AQB020SC@QFN8 [DX4005]
Z8F081ASB020EC@SOIC8 [DX1045]
Z8F081ASB020SC@SOIC8 [DX1045]
Z8F081ASH005EC@SOIC20 [DX1033]
Z8F081ASH005SC@SOIC20 [DX1033]
Z8F081ASJ020EC@SOIC28 [DX1033]
Z8F081ASJ020SC@SOIC28 [DX1033]
Z8F0821HH020EC@SSOP20 [DX1026]
Z8F0821HH020SC@SSOP20 [DX1026]
Z8F0821PH020EC [DX0001]
Z8F0821PH020SC [DX0001]
Z8F0822PJ020EC [DX0001]
Z8F0822PJ020SC [DX0001]
Z8F0822SJ020EC@SOIC28 [DX1033]
Z8F0822SJ020SC@SOIC28 [DX1033]
Z8F0823HH005EC@SSOP20 [DX1026]
Z8F0823HH005SC@SSOP20 [DX1026]
Z8F0823HJ020EC@SSOP28 [DX1026]
Z8F0823HJ020SC@SSOP28 [DX1026]
Z8F0823PB005EC [DX0001]
Z8F0823PB005SC [DX0001]
Z8F0823PH005EC [DX0001]
Z8F0823PH005SC [DX0001]
Z8F0823PJ020EC [DX0001]
Z8F0823PJ020SC [DX0001]

Z8F0813PH005EG [DX0001]
Z8F0813PH005SG [DX0001]
Z8F0813PJ020EG [DX0001]
Z8F0813PJ020SG [DX0001]
Z8F0813QB005EG@QFN8 [DX4005]
Z8F0813QB005SG@QFN8 [DX4005]
Z8F0813SB005EG@SOIC8 [DX1045]
Z8F0813SB005SG@SOIC8 [DX1045]
Z8F0813SH005EG@SOIC20 [DX1033]
Z8F0813SH005SG@SOIC20 [DX1033]
Z8F0813SJ020EG@SOIC28 [DX1033]
Z8F0813SJ020SG@SOIC28 [DX1033]
Z8F081AHH005EG@SSOP20 [DX1026]
Z8F081AHH005SG@SSOP20 [DX1026]
Z8F081AHJ020EG@SSOP28 [DX1026]
Z8F081AHJ020SG@SSOP28 [DX1026]
Z8F081APB020EG [DX0001]
Z8F081APB020SG [DX0001]
Z8F081APH005EG [DX0001]
Z8F081APH005SG [DX0001]
Z8F081APJ020EG [DX0001]
Z8F081APJ020SG [DX0001]
Z8F081AQB020EG@QFN8 [DX4005]
Z8F081AQB020SG@QFN8 [DX4005]
Z8F081ASB020EG@SOIC8 [DX1045]
Z8F081ASB020SG@SOIC8 [DX1045]
Z8F081ASH005EG@SOIC20 [DX1033]
Z8F081ASH005SG@SOIC20 [DX1033]
Z8F081ASJ020EG@SOIC28 [DX1033]
Z8F081ASJ020SG@SOIC28 [DX1033]
Z8F0821HH020EG@SSOP20 [DX1026]
Z8F0821HH020SG@SSOP20 [DX1026]
Z8F0821PH020EG [DX0001]
Z8F0821PH020SG [DX0001]
Z8F0822PJ020EG [DX0001]
Z8F0822PJ020SG [DX0001]
Z8F0822SJ020EG@SOIC28 [DX1033]
Z8F0822SJ020SG@SOIC28 [DX1033]
Z8F0823HH005EG@SSOP20 [DX1026]
Z8F0823HH005SG@SSOP20 [DX1026]
Z8F0823HJ020EG@SSOP28 [DX1026]
Z8F0823HJ020SG@SSOP28 [DX1026]
Z8F0823PB005EG [DX0001]
Z8F0823PB005SG [DX0001]
Z8F0823PH005EG [DX0001]
Z8F0823PH005SG [DX0001]
Z8F0823PJ020EG [DX0001]
Z8F0823PJ020SG [DX0001]

Z8F0823QB005EC@QFN8 [DX4005]
Z8F0823QB005SC@QFN8 [DX4005]
Z8F0823SB005EC@SOIC8 [DX1045]
Z8F0823SB005SC@SOIC8 [DX1045]
Z8F0823SH005EC@SOIC20 [DX1033]
Z8F0823SH005SC@SOIC20 [DX1033]
Z8F0823SJ020EC@SOIC28 [DX1033]
Z8F0823SJ020SC@SOIC28 [DX1033]
Z8F082AHH005EC@SSOP20 [DX1026]
Z8F082AHH005SC@SSOP20 [DX1026]
Z8F082AHJ020EC@SSOP28 [DX1026]
Z8F082AHJ020SC@SSOP28 [DX1026]
Z8F082APB020EC [DX0001]
Z8F082APB020SC [DX0001]
Z8F082APH005EC [DX0001]
Z8F082APH005SC [DX0001]
Z8F082APJ020EC [DX0001]
Z8F082APJ020SC [DX0001]
Z8F082AQB020EC@QFN8 [DX4005]
Z8F082AQB020SC@QFN8 [DX4005]
Z8F082ASB020EC@SOIC8 [DX1045]
Z8F082ASB020SC@SOIC8 [DX1045]
Z8F082ASH005EC@SOIC20 [DX1033]
Z8F082ASH005SC@SOIC20 [DX1033]
Z8F082ASJ020EC@SOIC28 [DX1033]
Z8F082ASJ020SC@SOIC28 [DX1033]
Z8F0830HH020EG@SSOP20 [DX1026]
Z8F0830HJ020EG@SSOP28 [DX1026]
Z8F0830PH020EG [DX0001]
Z8F0830PJ020EG [DX0001]
Z8F0830QH020EG@QFN20 [DX4025]
Z8F0830QJ020EG@QFN28 [DX4013]
Z8F0830SH020EG@SOIC20 [DX1033]
Z8F0830SJ020EG@SOIC28 [DX1033]
Z8F0831HH020EG@SSOP20 [DX1026]
Z8F0831HJ020EG@SSOP28 [DX1026]
Z8F0831PH020EG [DX0001]
Z8F0831PJ020EG [DX0001]
Z8F0831QH020EG@QFN20 [DX4025]
Z8F0831QJ020EG@QFN28 [DX4013]
Z8F0831SH020EG@SOIC20 [DX1033]
Z8F0831SJ020EG@SOIC28 [DX1033]
Z8F083AHH020EG@SSOP20 [DX1026]
Z8F083AHJ020EG@SSOP28 [DX1026]
Z8F083APH020EG [DX0001]
Z8F083APJ020EG [DX0001]
Z8F083AQH020EG@QFN20 [DX4025]
Z8F083AQJ020EG@QFN28 [DX4013]
Z8F0823QB005EG@QFN8 [DX4005]
Z8F0823QB005SG@QFN8 [DX4005]
Z8F0823SB005EG@SOIC8 [DX1045]
Z8F0823SB005SG@SOIC8 [DX1045]
Z8F0823SH005EG@SOIC20 [DX1033]
Z8F0823SH005SG@SOIC20 [DX1033]
Z8F0823SJ020EG@SOIC28 [DX1033]
Z8F0823SJ020SG@SOIC28 [DX1033]
Z8F082AHH005EG@SSOP20 [DX1026]
Z8F082AHH005SG@SSOP20 [DX1026]
Z8F082AHJ020EG@SSOP28 [DX1026]
Z8F082AHJ020SG@SSOP28 [DX1026]
Z8F082APB020EG [DX0001]
Z8F082APB020SG [DX0001]
Z8F082APH005EG [DX0001]
Z8F082APH005SG [DX0001]
Z8F082APJ020EG [DX0001]
Z8F082APJ020SG [DX0001]
Z8F082AQB020EG@QFN8 [DX4005]
Z8F082AQB020SG@QFN8 [DX4005]
Z8F082ASB020EG@SOIC8 [DX1045]
Z8F082ASB020SG@SOIC8 [DX1045]
Z8F082ASH005EG@SOIC20 [DX1033]
Z8F082ASH005SG@SOIC20 [DX1033]
Z8F082ASJ020EG@SOIC28 [DX1033]
Z8F082ASJ020SG@SOIC28 [DX1033]
Z8F0830HH020SG@SSOP20 [DX1026]
Z8F0830HJ020SG@SSOP28 [DX1026]
Z8F0830PH020SG [DX0001]
Z8F0830PJ020SG [DX0001]
Z8F0830QH020SG@QFN20 [DX4025]
Z8F0830QJ020SG@QFN28 [DX4013]
Z8F0830SH020SG@SOIC20 [DX1033]
Z8F0830SJ020SG@SOIC28 [DX1033]
Z8F0831HH020SG@SSOP20 [DX1026]
Z8F0831HJ020SG@SSOP28 [DX1026]
Z8F0831PH020SG [DX0001]
Z8F0831PJ020SG [DX0001]
Z8F0831QH020SG@QFN20 [DX4025]
Z8F0831QJ020SG@QFN28 [DX4013]
Z8F0831SH020SG@SOIC20 [DX1033]
Z8F0831SJ020SG@SOIC28 [DX1033]
Z8F083AHH020SG@SSOP20 [DX1026]
Z8F083AHJ020SG@SSOP28 [DX1026]
Z8F083APH020SG [DX0001]
Z8F083APJ020SG [DX0001]
Z8F083AQH020SG@QFN20 [DX4025]
Z8F083AQJ020SG@QFN28 [DX4013]

Z8F083ASH020EG@SOIC20 [DX1033]
Z8F083ASJ020EG@SOIC28 [DX1033]
Z8F0880AN020EG@QFP44 [DX3005]
Z8F0880HH020EG@SSOP20 [DX1026]
Z8F0880HJ020EG@SSOP28 [DX1026]
Z8F0880PH020EG [DX0001]
Z8F0880PJ020EG [DX0001]
Z8F0880PM020EG [DX0001]
Z8F0880QN020EG@QFN44 [DX4018]
Z8F0880SH020EG@SOIC20 [DX1033]
Z8F0880SJ020EG@SOIC28 [DX1033]
Z8F1232HH020EG@SSOP20 [DX1026]
Z8F1232HJ020EG@SSOP28 [DX1026]
Z8F1232PH020EG [DX0001]
Z8F1232PJ020EG [DX0001]
Z8F1232QH020EG@QFN20 [DX4025]
Z8F1232QJ020EG@QFN28 [DX4013]
Z8F1232SH020EG@SOIC20 [DX1033]
Z8F1232SJ020EG@SOIC28 [DX1033]
Z8F1233HH020EG@SSOP20 [DX1026]
Z8F1233HJ020EG@SSOP28 [DX1026]
Z8F1233PH020EG [DX0001]
Z8F1233PJ020EG [DX0001]
Z8F1233QH020EG@QFN20 [DX4025]
Z8F1233QJ020EG@QFN28 [DX4013]
Z8F1233SH020EG@SOIC20 [DX1033]
Z8F1233SJ020EG@SOIC28 [DX1033]
Z8F1601AN020EC@LQFP44 [DX3005]
Z8F1601AN020SC@LQFP44 [DX3005]
Z8F1601PM020EC [DX0001]
Z8F1601PM020SC [DX0001]
Z8F1601VN020EC@PLCC44 [DX2044]
Z8F1601VN020SC@PLCC44 [DX2044]
Z8F1602AN020EC@LQFP44 [DX3005]
Z8F1602AN020SC@LQFP44 [DX3005]
Z8F1602PM020EC [DX0001]
Z8F1602PM020SC [DX0001]
Z8F1602VN020EC@PLCC44 [DX2044]
Z8F1602VN020SC@PLCC44 [DX2044]
Z8F1621AN020AC@LQFP44 [DX3005]
Z8F1621AN020EC@LQFP44 [DX3005]
Z8F1621AN020SC@LQFP44 [DX3005]
Z8F1621PM020AC [DX0001]
Z8F1621PM020EC [DX0001]
Z8F1621PM020SC [DX0001]
Z8F1621VN020AC@PLCC44 [DX2044]
Z8F1621VN020EC@PLCC44 [DX2044]
Z8F1621VN020SC@PLCC44 [DX2044]
Z8F083ASH020SG@SOIC20 [DX1033]
Z8F083ASJ020SG@SOIC28 [DX1033]
Z8F0880AN020SG@QFP44 [DX3005]
Z8F0880HH020SG@SSOP20 [DX1026]
Z8F0880HJ020SG@SSOP28 [DX1026]
Z8F0880PH020SG [DX0001]
Z8F0880PJ020SG [DX0001]
Z8F0880PM020SG [DX0001]
Z8F0880QN020SG@QFN44 [DX4018]
Z8F0880SH020SG@SOIC20 [DX1033]
Z8F0880SJ020SG@SOIC28 [DX1033]
Z8F1232HH020SG@SSOP20 [DX1026]
Z8F1232HJ020SG@SSOP28 [DX1026]
Z8F1232PH020SG [DX0001]
Z8F1232PJ020SG [DX0001]
Z8F1232QH020SG@QFN20 [DX4025]
Z8F1232QJ020SG@QFN28 [DX4013]
Z8F1232SH020SG@SOIC20 [DX1033]
Z8F1232SJ020SG@SOIC28 [DX1033]
Z8F1233HH020SG@SSOP20 [DX1026]
Z8F1233HJ020SG@SSOP28 [DX1026]
Z8F1233PH020SG [DX0001]
Z8F1233PJ020SG [DX0001]
Z8F1233QH020SG@QFN20 [DX4025]
Z8F1233QJ020SG@QFN28 [DX4013]
Z8F1233SH020SG@SOIC20 [DX1033]
Z8F1233SJ020SG@SOIC28 [DX1033]
Z8F1601AN020EG@LQFP44 [DX3005]
Z8F1601AN020SG@LQFP44 [DX3005]
Z8F1601PM020EG [DX0001]
Z8F1601PM020SG [DX0001]
Z8F1601VN020EG@PLCC44 [DX2044]
Z8F1601VN020SG@PLCC44 [DX2044]
Z8F1602AN020EG@LQFP44 [DX3005]
Z8F1602AN020SG@LQFP44 [DX3005]
Z8F1602PM020EG [DX0001]
Z8F1602PM020SG [DX0001]
Z8F1602VN020EG@PLCC44 [DX2044]
Z8F1602VN020SG@PLCC44 [DX2044]
Z8F1621AN020AG@LQFP44 [DX3005]
Z8F1621AN020EG@LQFP44 [DX3005]
Z8F1621AN020SG@LQFP44 [DX3005]
Z8F1621PM020AG [DX0001]
Z8F1621PM020EG [DX0001]
Z8F1621PM020SG [DX0001]
Z8F1621VN020AG@PLCC44 [DX2044]
Z8F1621VN020EG@PLCC44 [DX2044]
Z8F1621VN020SG@PLCC44 [DX2044]

Z8F1622AR020AC@LQFP64 [DX3011]
Z8F1622AR020EC@LQFP64 [DX3011]
Z8F1622AR020SC@LQFP64 [DX3011]
Z8F1622VS020AC@PLCC68 [DX2068]
Z8F1622VS020EC@PLCC68 [DX2068]
Z8F1622VS020SC@PLCC68 [DX2068]
Z8F1680AN020EG@QFP44 [DX3005]
Z8F1680HH020EG@SSOP20 [DX1026]
Z8F1680HJ020EG@SSOP28 [DX1026]
Z8F1680PH020EG [DX0001]
Z8F1680PJ020EG [DX0001]
Z8F1680PM020EG [DX0001]
Z8F1680QN020EG@QFN44 [DX4018]
Z8F1680SH020EG@SOIC20 [DX1033]
Z8F1680SJ020EG@SOIC28 [DX1033]
Z8F2421AN020AC@LQFP44 [DX3005]
Z8F2421AN020EC@LQFP44 [DX3005]
Z8F2421AN020SC@LQFP44 [DX3005]
Z8F2421PM020AC [DX0001]
Z8F2421PM020EC [DX0001]
Z8F2421PM020SC [DX0001]
Z8F2421VN020AC@PLCC44 [DX2044]
Z8F2421VN020EC@PLCC44 [DX2044]
Z8F2421VN020SC@PLCC44 [DX2044]
Z8F2422AR020AC@LQFP64 [DX3011]
Z8F2422AR020EC@LQFP64 [DX3011]
Z8F2422AR020SC@LQFP64 [DX3011]
Z8F2422VS020AC@PLCC68 [DX2068]
Z8F2422VS020EC@PLCC68 [DX2068]
Z8F2422VS020SC@PLCC68 [DX2068]
Z8F2480AN020EG@QFP44 [DX3005]
Z8F2480HH020EG@SSOP20 [DX1026]
Z8F2480HJ020EG@SSOP28 [DX1026]
Z8F2480PH020EG [DX0001]
Z8F2480PJ020EG [DX0001]
Z8F2480PM020EG [DX0001]
Z8F2480QN020EG@QFN44 [DX4018]
Z8F2480SH020EG@SOIC20 [DX1033]
Z8F2480SJ020EG@SOIC28 [DX1033]
Z8F3221AN020AC@LQFP44 [DX3005]
Z8F3221AN020EC@LQFP44 [DX3005]
Z8F3221AN020SC@LQFP44 [DX3005]
Z8F3221PM020AC [DX0001]
Z8F3221PM020EC [DX0001]
Z8F3221PM020SC [DX0001]
Z8F3221VN020AC@PLCC44 [DX2044]
Z8F3221VN020EC@PLCC44 [DX2044]
Z8F3221VN020SC@PLCC44 [DX2044]
Z8F1622AR020AG@LQFP64 [DX3011]
Z8F1622AR020EG@LQFP64 [DX3011]
Z8F1622AR020SG@LQFP64 [DX3011]
Z8F1622VS020AG@PLCC68 [DX2068]
Z8F1622VS020EG@PLCC68 [DX2068]
Z8F1622VS020SG@PLCC68 [DX2068]
Z8F1680AN020SG@QFP44 [DX3005]
Z8F1680HH020SG@SSOP20 [DX1026]
Z8F1680HJ020SG@SSOP28 [DX1026]
Z8F1680PH020SG [DX0001]
Z8F1680PJ020SG [DX0001]
Z8F1680PM020SG [DX0001]
Z8F1680QN020SG@QFN44 [DX4018]
Z8F1680SH020SG@SOIC20 [DX1033]
Z8F1680SJ020SG@SOIC28 [DX1033]
Z8F2421AN020AG@LQFP44 [DX3005]
Z8F2421AN020EG@LQFP44 [DX3005]
Z8F2421AN020SG@LQFP44 [DX3005]
Z8F2421PM020AG [DX0001]
Z8F2421PM020EG [DX0001]
Z8F2421PM020SG [DX0001]
Z8F2421VN020AG@PLCC44 [DX2044]
Z8F2421VN020EG@PLCC44 [DX2044]
Z8F2421VN020SG@PLCC44 [DX2044]
Z8F2422AR020AG@LQFP64 [DX3011]
Z8F2422AR020EG@LQFP64 [DX3011]
Z8F2422AR020SG@LQFP64 [DX3011]
Z8F2422VS020AG@PLCC68 [DX2068]
Z8F2422VS020EG@PLCC68 [DX2068]
Z8F2422VS020SG@PLCC68 [DX2068]
Z8F2480AN020SG@QFP44 [DX3005]
Z8F2480HH020SG@SSOP20 [DX1026]
Z8F2480HJ020SG@SSOP28 [DX1026]
Z8F2480PH020SG [DX0001]
Z8F2480PJ020SG [DX0001]
Z8F2480PM020SG [DX0001]
Z8F2480QN020SG@QFN44 [DX4018]
Z8F2480SH020SG@SOIC20 [DX1033]
Z8F2480SJ020SG@SOIC28 [DX1033]
Z8F3221AN020AG@LQFP44 [DX3005]
Z8F3221AN020EG@LQFP44 [DX3005]
Z8F3221AN020SG@LQFP44 [DX3005]
Z8F3221PM020AG [DX0001]
Z8F3221PM020EG [DX0001]
Z8F3221PM020SG [DX0001]
Z8F3221VN020AG@PLCC44 [DX2044]
Z8F3221VN020EG@PLCC44 [DX2044]
Z8F3221VN020SG@PLCC44 [DX2044]

Z8F3222AR020AC@LQFP64 [DX3011]
Z8F3222AR020AG@LQFP64 [DX3011]
Z8F3222AR020EC@LQFP64 [DX3011]
Z8F3222AR020EG@LQFP64 [DX3011]
Z8F3222AR020SC@LQFP64 [DX3011]
Z8F3222AR020SG@LQFP64 [DX3011]
Z8F3222VS020AC@PLCC68 [DX2068]
Z8F3222VS020AG@PLCC68 [DX2068]
Z8F3222VS020EC@PLCC68 [DX2068]
Z8F3222VS020EG@PLCC68 [DX2068]
Z8F3222VS020SC@PLCC68 [DX2068]
Z8F3222VS020SG@PLCC68 [DX2068]
Z8F3280AN020EG@QFP44 [DX3005]
Z8F3280AN020SG@QFP44 [DX3005]
Z8F3280HH020EG@SSOP20 [DX1026]
Z8F3280HH020SG@SSOP20 [DX1026]
Z8F3280HJ020EG@SSOP28 [DX1026]
Z8F3280HJ020SG@SSOP28 [DX1026]
Z8F3280PH020EG [DX0001]
Z8F3280PH020SG [DX0001]
Z8F3280PJ020EG [DX0001]
Z8F3280PJ020SG [DX0001]
Z8F3280PM020EG [DX0001]
Z8F3280PM020SG [DX0001]
Z8F3280QN020EG@QFN44 [DX4018]
Z8F3280QN020SG@QFN44 [DX4018]
Z8F3280SH020EG@SOIC20 [DX1033]
Z8F3280SH020SG@SOIC20 [DX1033]
Z8F3280SJ020EG@SOIC28 [DX1033]
Z8F3280SJ020SG@SOIC28 [DX1033]
Z8F4801AN@TQFP44 [DX3005]
Z8F4801PM [DX0001]
Z8F4801VN@PLCC44 [DX2044]
Z8F4802AR020SC@LQFP64 [DX3011]
Z8F4821AN020AC@LQFP44 [DX3005]
Z8F4821AN020AG@LQFP44 [DX3005]
Z8F4821AN020EC@LQFP44 [DX3005]
Z8F4821AN020EG@LQFP44 [DX3005]
Z8F4821AN020EG21@LQFP44 [DX3005]
Z8F4821AN020SC@LQFP44 [DX3005]
Z8F4821AN020SG@LQFP44 [DX3005]
Z8F4821AN020SG21@LQFP44 [DX3005]
Z8F4821PM020AC [DX0001]
Z8F4821PM020AG [DX0001]
Z8F4821PM020EC [DX0001]
Z8F4821PM020EG [DX0001]
Z8F4821PM020SC [DX0001]
Z8F4821PM020SG [DX0001]
Z8F4821VN020AC@PLCC44 [DX2044]
Z8F4821VN020AG@PLCC44 [DX2044]
Z8F4821VN020EC@PLCC44 [DX2044]
Z8F4821VN020EG@PLCC44 [DX2044]
Z8F4821VN020SC@PLCC44 [DX2044]
Z8F4821VN020SG@PLCC44 [DX2044]
Z8F4822AR020AC@LQFP64 [DX3011]
Z8F4822AR020AG@LQFP64 [DX3011]
Z8F4822AR020EC@LQFP64 [DX3011]
Z8F4822AR020EG@LQFP64 [DX3011]
Z8F4822AR020SC@LQFP64 [DX3011]
Z8F4822AR020SG@LQFP64 [DX3011]
Z8F4822VS020AC@PLCC68 [DX2068]
Z8F4822VS020AG@PLCC68 [DX2068]
Z8F4822VS020EC@PLCC68 [DX2068]
Z8F4822VS020EG@PLCC68 [DX2068]
Z8F4822VS020SC@PLCC68 [DX2068]
Z8F4822VS020SG@PLCC68 [DX2068]
Z8F4823FT020AC@QFP80 [DX3019]
Z8F4823FT020AG@QFP80 [DX3019]
Z8F4823FT020EC@QFP80 [DX3019]
Z8F4823FT020EG@QFP80 [DX3019]
Z8F4823FT020SC@QFP80 [DX3019]
Z8F4823FT020SG@QFP80 [DX3019]
Z8F6401AN@TQFP44 [DX3005]
Z8F6401PM [DX0001]
Z8F6401VN@PLCC44 [DX2044]
Z8F6402AR020EC@LQFP64 [DX3011]
Z8F6402AR020SC@LQFP64 [DX3011]
Z8F6402VS020EC@PLCC68 [DX2068]
Z8F6402VS020SC@PLCC68 [DX2068]
Z8F6403FT020EC@QFP80 [DX3019]
Z8F6403FT020SC@QFP80 [DX3019]
Z8F6421AN020AC@LQFP44 [DX3005]
Z8F6421AN020AG@LQFP44 [DX3005]
Z8F6421AN020EC@LQFP44 [DX3005]
Z8F6421AN020EG@LQFP44 [DX3005]
Z8F6421AN020SC@LQFP44 [DX3005]
Z8F6421AN020SG@LQFP44 [DX3005]
Z8F6421PM020AC [DX0001]
Z8F6421PM020AG [DX0001]
Z8F6421PM020EC [DX0001]
Z8F6421PM020EG [DX0001]
Z8F6421PM020SC [DX0001]
Z8F6421PM020SG [DX0001]
Z8F6421VN020AC@PLCC44 [DX2044]
Z8F6421VN020AG@PLCC44
Z8F6421VN020EC@PLCC44 [DX2044]

Z8F6421VN020EG@PLCC44
Z8F6421VN020SG@PLCC44
Z8F6422AR020AG@LQFP64 [DX3011]
Z8F6422AR020EG@LQFP64 [DX3011]
Z8F6422AR020SG@LQFP64 [DX3011]
Z8F6422VS020AG@PLCC68 [DX2068]
Z8F6422VS020EG@PLCC68 [DX2068]
Z8F6422VS020SG@PLCC68 [DX2068]
Z8F6423FT020AG@QFP80 [DX3019]
Z8F6423FT020EG@QFP80 [DX3019]
Z8F6423FT020SG@QFP80 [DX3019]
Z8FMC04100AKEG@QFP32 [DX3001]
Z8FMC04100AKSG@QFP32 [DX3001]
Z8FMC04100QKEG@QFN32 [DX4015]
Z8FMC04100QKSG@QFN32 [DX4015]
Z8FMC08100AKEG@QFP32 [DX3001]
Z8FMC08100AKSG@QFP32 [DX3001]
Z8FMC08100QKEG@QFN32 [DX4015]
Z8FMC08100QKSG@QFN32 [DX4015]
Z8FMC16100AKEG@QFP32 [DX3001]
Z8FMC16100AKSG@QFP32 [DX3001]
Z8FMC16100QKEG@QFN32 [DX4015]
Z8FMC16100QKSG@QFN32 [DX4015]
Z8FMC32100AKEG@QFP32 [DX3001]
Z8FMC32100AKSG@QFP32 [DX3001]
Z8FMC32100QKEG@QFN32 [DX4015]
Z8FMC32100QKSG@QFN32 [DX4015]
Z8FMC64100AKEG@QFP32 [DX3001]
Z8FMC64100AKSG@QFP32 [DX3001]
Z8FMC64100QKEG@QFN32 [DX4015]
Z8FMC64100QKSG@QFN32 [DX4015]
Z8FS011APB020EG [DX0001]
Z8FS011APB020SG [DX0001]
Z8FS011AQB020EG [DX4005]
Z8FS011AQB020SG [DX4005]
Z8FS011ASB020EG [DX1045]
Z8FS011ASB020SG [DX1045]
Z8FS012APB020EG [DX0001]
Z8FS012APB020SG [DX0001]
Z8FS012AQB020EG [DX4005]
Z8FS012AQB020SG [DX4005]
Z8FS012ASB020EG [DX1045]
Z8FS012ASB020SG [DX1045]
Z8FS0213HH005EG [DX1026]
Z8FS0213HH005SG [DX1026]
Z8FS0213HJ005EG [DX1026]
Z8FS0213HJ005SG [DX1026]
Z8FS0213PH005EG [DX0001]
Z8F6421VN020SC@PLCC44 [DX2044]
Z8F6422AR020AC@LQFP64 [DX3011]
Z8F6422AR020EC@LQFP64 [DX3011]
Z8F6422AR020SC@LQFP64 [DX3011]
Z8F6422VS020AC@PLCC68 [DX2068]
Z8F6422VS020EC@PLCC68 [DX2068]
Z8F6422VS020SC@PLCC68 [DX2068]
Z8F6423FT020AC@QFP80 [DX3019]
Z8F6423FT020EC@QFP80 [DX3019]
Z8F6423FT020SC@QFP80 [DX3019]
Z8FMC04100AKEC [DX3001]
Z8FMC04100AKSC [DX3001]
Z8FMC04100QKEC [DX4015]
Z8FMC04100QKSC [DX4015]
Z8FMC08100AKEC [DX3001]
Z8FMC08100AKSC [DX3001]
Z8FMC08100QKEC [DX4015]
Z8FMC08100QKSC [DX4015]
Z8FMC16100AKEC [DX3001]
Z8FMC16100AKSC [DX3001]
Z8FMC16100QKEC [DX4015]
Z8FMC16100QKSC [DX4015]
Z8FMC32100AKEC [DX3001]
Z8FMC32100AKSC [DX3001]
Z8FMC32100QKEC [DX4015]
Z8FMC32100QKSC [DX4015]
Z8FMC64100AKEC [DX3001]
Z8FMC64100AKSC [DX3001]
Z8FMC64100QKEC [DX4015]
Z8FMC64100QKSC [DX4015]
Z8FS011APB020EC [DX0001]
Z8FS011APB020SC [DX0001]
Z8FS011AQB020EC [DX4005]
Z8FS011AQB020SC [DX4005]
Z8FS011ASB020EC [DX1045]
Z8FS011ASB020SC [DX1045]
Z8FS012APB020EC [DX0001]
Z8FS012APB020SC [DX0001]
Z8FS012AQB020EC [DX4005]
Z8FS012AQB020SC [DX4005]
Z8FS012ASB020EC [DX1045]
Z8FS012ASB020SC [DX1045]
Z8FS0213HH005EC [DX1026]
Z8FS0213HH005SC [DX1026]
Z8FS0213HJ005EC [DX1026]
Z8FS0213HJ005SC [DX1026]
Z8FS0213PH005EC [DX0001]
Z8FS0213PH005SC [DX0001]

Z8FS0213PH005SG [DX0001]
Z8FS0213PJ005EG [DX0001]
Z8FS0213PJ005SG [DX0001]
Z8FS0213SH005EG [DX1033]
Z8FS0213SH005SG [DX1033]
Z8FS0213SJ005EG [DX1033]
Z8FS0213SJ005SG [DX1033]
Z8FS021AHH020EG [DX1026]
Z8FS021AHH020SG [DX1026]
Z8FS021AHJ020EG [DX1026]
Z8FS021AHJ020SG [DX1026]
Z8FS021APB020EG [DX0001]
Z8FS021APB020SG [DX0001]
Z8FS021APH020EG [DX0001]
Z8FS021APH020SG [DX0001]
Z8FS021APJ020EG [DX0001]
Z8FS021APJ020SG [DX0001]
Z8FS021AQB020EG [DX4005]
Z8FS021AQB020SG [DX4005]
Z8FS021ASB020EG [DX1045]
Z8FS021ASB020SG [DX1045]
Z8FS021ASH020EG [DX1033]
Z8FS021ASH020SG [DX1033]
Z8FS021ASJ020EG [DX1033]
Z8FS021ASJ020SG [DX1033]
Z8FS022APB020EG [DX0001]
Z8FS022APB020SG [DX0001]
Z8FS022AQB020EG [DX4005]
Z8FS022AQB020SG [DX4005]
Z8FS022ASB020EG [DX1045]
Z8FS022ASB020SG [DX1045]
Z8FS040BPB020EG [DX0001]
Z8FS040BPB020SG [DX0001]
Z8FS040BQB020EG [DX4005]
Z8FS040BQB020SG [DX4005]
Z8FS040BSB020EG [DX1045]
Z8FS040BSB020SG [DX1045]
Z8FS041APB020EG [DX0001]
Z8FS041APB020SG [DX0001]
Z8FS041AQB020EG [DX4005]
Z8FS041AQB020SG [DX4005]
Z8FS041ASB020EG [DX1045]
Z8FS041ASB020SG [DX1045]
Z8FS042APB020EG [DX0001]
Z8FS042APB020SG [DX0001]
Z8FS042AQB020EG [DX4005]
Z8FS042AQB020SG [DX4005]
Z8FS042ASB020EG [DX1045]
Z8FS0213PJ005EC [DX0001]
Z8FS0213PJ005SC [DX0001]
Z8FS0213SH005EC [DX1033]
Z8FS0213SH005SC [DX1033]
Z8FS0213SJ005EC [DX1033]
Z8FS0213SJ005SC [DX1033]
Z8FS021AHH020EC [DX1026]
Z8FS021AHH020SC [DX1026]
Z8FS021AHJ020EC [DX1026]
Z8FS021AHJ020SC [DX1026]
Z8FS021APB020EC [DX0001]
Z8FS021APB020SC [DX0001]
Z8FS021APH020EC [DX0001]
Z8FS021APH020SC [DX0001]
Z8FS021APJ020EC [DX0001]
Z8FS021APJ020SC [DX0001]
Z8FS021AQB020EC [DX4005]
Z8FS021AQB020SC [DX4005]
Z8FS021ASB020EC [DX1045]
Z8FS021ASB020SC [DX1045]
Z8FS021ASH020EC [DX1033]
Z8FS021ASH020SC [DX1033]
Z8FS021ASJ020EC [DX1033]
Z8FS021ASJ020SC [DX1033]
Z8FS022APB020EC [DX0001]
Z8FS022APB020SC [DX0001]
Z8FS022AQB020EC [DX4005]
Z8FS022AQB020SC [DX4005]
Z8FS022ASB020EC [DX1045]
Z8FS022ASB020SC [DX1045]
Z8FS040BPB020EC [DX0001]
Z8FS040BPB020SC [DX0001]
Z8FS040BQB020EC [DX4005]
Z8FS040BQB020SC [DX4005]
Z8FS040BSB020EC [DX1045]
Z8FS040BSB020SC [DX1045]
Z8FS041APB020EC [DX0001]
Z8FS041APB020SC [DX0001]
Z8FS041AQB020EC [DX4005]
Z8FS041AQB020SC [DX4005]
Z8FS041ASB020EC [DX1045]
Z8FS041ASB020SC [DX1045]
Z8FS042APB020EC [DX0001]
Z8FS042APB020SC [DX0001]
Z8FS042AQB020EC [DX4005]
Z8FS042AQB020SC [DX4005]
Z8FS042ASB020EC [DX1045]
Z8FS042ASB020SC [DX1045]

Z8FS042ASB020SG [DX1045]
Z8FS081APB020EG [DX0001]
Z8FS081APB020SG [DX0001]
Z8FS081AQB020EG [DX4005]
Z8FS081AQB020SG [DX4005]
Z8FS081ASB020EG [DX1045]
Z8FS081ASB020SG [DX1045]
Z8FS082APB020EG [DX0001]
Z8FS082APB020SG [DX0001]
Z8FS082AQB020EG [DX4005]
Z8FS082AQB020SG [DX4005]
Z8FS082ASB020EG [DX1045]
Z8FS082ASB020SG [DX1045]
Z8PE00210HSC@SSOP20 [DX1001]
Z8PE00210PSC [DX0001]
Z8PE00210SSC@SOIC18 [DX1033]
Z8PE00310HEC@SSOP20 [DX1001]
Z8PE00310PEC [DX0001]
Z8PE00310SEC@SOIC18 [DX1033]
Z8PE00310SSG@SOIC18 [DX1033]
ZGP323HAH2004G@SSOP20 [DX1026]
ZGP323HAH2008G@SSOP20 [DX1026]
ZGP323HAH2016G@SSOP20 [DX1026]
ZGP323HAH2032G@SSOP20 [DX1026]
ZGP323HAH2804G@SSOP28 [DX1026]
ZGP323HAH2808G@SSOP28 [DX1026]
ZGP323HAH2816G@SSOP28 [DX1026]
ZGP323HAH2832G@SSOP28 [DX1026]
ZGP323HAH4804G@SSOP48 [DX1028]
ZGP323HAH4808G@SSOP48 [DX1028]
ZGP323HAH4816G@SSOP48 [DX1028]
ZGP323HAH4832G@SSOP48 [DX1028]
ZGP323HAP2004G [DX0001]
ZGP323HAP2008G [DX0001]
ZGP323HAP2016G [DX0001]
ZGP323HAP2032G [DX0001]
ZGP323HAP2804G [DX0001]
ZGP323HAP2808G [DX0001]
ZGP323HAP2816G [DX0001]
ZGP323HAP2832G [DX0001]
ZGP323HAP4004G [DX0001]
ZGP323HAP4008G [DX0001]
ZGP323HAP4016G [DX0001]
ZGP323HAP4032G [DX0001]
ZGP323HAS2004G@SOIC20 [DX1033]
ZGP323HAS2008G@SOIC20 [DX1033]
ZGP323HAS2016G@SOIC20 [DX1033]
ZGP323HAS2032G@SOIC20 [DX1033]
Z8FS081APB020EC [DX0001]
Z8FS081APB020SC [DX0001]
Z8FS081AQB020EC [DX4005]
Z8FS081AQB020SC [DX4005]
Z8FS081ASB020EC [DX1045]
Z8FS081ASB020SC [DX1045]
Z8FS082APB020EC [DX0001]
Z8FS082APB020SC [DX0001]
Z8FS082AQB020EC [DX4005]
Z8FS082AQB020SC [DX4005]
Z8FS082ASB020EC [DX1045]
Z8FS082ASB020SC [DX1045]
Z8PE00210HEC@SSOP20 [DX1001]
Z8PE00210PEC [DX0001]
Z8PE00210SEC@SOIC18 [DX1033]
Z8PE00210SSG@SOIC18 [DX1033]
Z8PE00310HSC@SSOP20 [DX1001]
Z8PE00310PSC [DX0001]
Z8PE00310SSC@SOIC18 [DX1033]
ZGP323HAH2004C@SSOP20 [DX1026]
ZGP323HAH2008C@SSOP20 [DX1026]
ZGP323HAH2016C@SSOP20 [DX1026]
ZGP323HAH2032C@SSOP20 [DX1026]
ZGP323HAH2804C@SSOP28 [DX1026]
ZGP323HAH2808C@SSOP28 [DX1026]
ZGP323HAH2816C@SSOP28 [DX1026]
ZGP323HAH2832C@SSOP28 [DX1026]
ZGP323HAH4804C@SSOP48 [DX1028]
ZGP323HAH4808C@SSOP48 [DX1028]
ZGP323HAH4816C@SSOP48 [DX1028]
ZGP323HAH4832C@SSOP48 [DX1028]
ZGP323HAP2004C [DX0001]
ZGP323HAP2008C [DX0001]
ZGP323HAP2016C [DX0001]
ZGP323HAP2032C [DX0001]
ZGP323HAP2804C [DX0001]
ZGP323HAP2808C [DX0001]
ZGP323HAP2816C [DX0001]
ZGP323HAP2832C [DX0001]
ZGP323HAP4004C [DX0001]
ZGP323HAP4008C [DX0001]
ZGP323HAP4016C [DX0001]
ZGP323HAP4032C [DX0001]
ZGP323HAS2004C@SOIC20 [DX1033]
ZGP323HAS2008C@SOIC20 [DX1033]
ZGP323HAS2016C@SOIC20 [DX1033]
ZGP323HAS2032C@SOIC20 [DX1033]
ZGP323HAS2804C@SOIC28 [DX1033]

ZGP323HAS2804G@SOIC28 [DX1033]
ZGP323HAS2808G@SOIC28 [DX1033]
ZGP323HAS2816G@SOIC28 [DX1033]
ZGP323HAS2832G@SOIC28 [DX1033]
ZGP323HEH2004G@SSOP20 [DX1026]
ZGP323HEH2008G@SSOP20 [DX1026]
ZGP323HEH2016G@SSOP20 [DX1026]
ZGP323HEH2032G@SSOP20 [DX1026]
ZGP323HEH2804G@SSOP28 [DX1026]
ZGP323HEH2808G@SSOP28 [DX1026]
ZGP323HEH2816G@SSOP28 [DX1026]
ZGP323HEH2832G@SSOP28 [DX1026]
ZGP323HEH4804G@SSOP48 [DX1028]
ZGP323HEH4808G@SSOP48 [DX1028]
ZGP323HEH4816G@SSOP48 [DX1028]
ZGP323HEH4832G@SSOP48 [DX1028]
ZGP323HEP2004G [DX0001]
ZGP323HEP2008G [DX0001]
ZGP323HEP2016G [DX0001]
ZGP323HEP2032G [DX0001]
ZGP323HEP2804G [DX0001]
ZGP323HEP2808G [DX0001]
ZGP323HEP2816G [DX0001]
ZGP323HEP2832G [DX0001]
ZGP323HEP4004G [DX0001]
ZGP323HEP4008G [DX0001]
ZGP323HEP4016G [DX0001]
ZGP323HEP4032G [DX0001]
ZGP323HES2004G@SOIC20 [DX1033]
ZGP323HES2008G@SOIC20 [DX1033]
ZGP323HES2016G@SOIC20 [DX1033]
ZGP323HES2032G@SOIC20 [DX1033]
ZGP323HES2804G@SOIC28 [DX1033]
ZGP323HES2808G@SOIC28 [DX1033]
ZGP323HES2816G@SOIC28 [DX1033]
ZGP323HES2832G@SOIC28 [DX1033]
ZGP323HSH2004G@SSOP20 [DX1026]
ZGP323HSH2008G@SSOP20 [DX1026]
ZGP323HSH2016G@SSOP20 [DX1026]
ZGP323HSH2032G@SSOP20 [DX1026]
ZGP323HSH2804G@SSOP28 [DX1026]
ZGP323HSH2808G@SSOP28 [DX1026]
ZGP323HSH2816G@SSOP28 [DX1026]
ZGP323HSH2832G@SSOP28 [DX1026]
ZGP323HSH4804G@SSOP48 [DX1028]
ZGP323HSH4808G@SSOP48 [DX1028]
ZGP323HSH4816G@SSOP48 [DX1028]
ZGP323HSH4832G@SSOP48 [DX1028]
ZGP323HAS2808C@SOIC28 [DX1033]
ZGP323HAS2816C@SOIC28 [DX1033]
ZGP323HAS2832C@SOIC28 [DX1033]
ZGP323HEH2004C@SSOP20 [DX1026]
ZGP323HEH2008C@SSOP20 [DX1026]
ZGP323HEH2016C@SSOP20 [DX1026]
ZGP323HEH2032C@SSOP20 [DX1026]
ZGP323HEH2804C@SSOP28 [DX1026]
ZGP323HEH2808C@SSOP28 [DX1026]
ZGP323HEH2816C@SSOP28 [DX1026]
ZGP323HEH2832C@SSOP28 [DX1026]
ZGP323HEH4804C@SSOP48 [DX1028]
ZGP323HEH4808C@SSOP48 [DX1028]
ZGP323HEH4816C@SSOP48 [DX1028]
ZGP323HEH4832C@SSOP48 [DX1028]
ZGP323HEP2004C [DX0001]
ZGP323HEP2008C [DX0001]
ZGP323HEP2016C [DX0001]
ZGP323HEP2032C [DX0001]
ZGP323HEP2804C [DX0001]
ZGP323HEP2808C [DX0001]
ZGP323HEP2816C [DX0001]
ZGP323HEP2832C [DX0001]
ZGP323HEP4004C [DX0001]
ZGP323HEP4008C [DX0001]
ZGP323HEP4016C [DX0001]
ZGP323HEP4032C [DX0001]
ZGP323HES2004C@SOIC20 [DX1033]
ZGP323HES2008C@SOIC20 [DX1033]
ZGP323HES2016C@SOIC20 [DX1033]
ZGP323HES2032C@SOIC20 [DX1033]
ZGP323HES2804C@SOIC28 [DX1033]
ZGP323HES2808C@SOIC28 [DX1033]
ZGP323HES2816C@SOIC28 [DX1033]
ZGP323HES2832C@SOIC28 [DX1033]
ZGP323HSH2004C@SSOP20 [DX1026]
ZGP323HSH2008C@SSOP20 [DX1026]
ZGP323HSH2016C@SSOP20 [DX1026]
ZGP323HSH2032C@SSOP20 [DX1026]
ZGP323HSH2804C@SSOP28 [DX1026]
ZGP323HSH2808C@SSOP28 [DX1026]
ZGP323HSH2816C@SSOP28 [DX1026]
ZGP323HSH2832C@SSOP28 [DX1026]
ZGP323HSH4804C@SSOP48 [DX1028]
ZGP323HSH4808C@SSOP48 [DX1028]
ZGP323HSH4816C@SSOP48 [DX1028]
ZGP323HSH4832C@SSOP48 [DX1028]
ZGP323HSP2004C [DX0001]

ZGP323HSP2004G [DX0001]
ZGP323HSP2008G [DX0001]
ZGP323HSP2016G [DX0001]
ZGP323HSP2032G [DX0001]
ZGP323HSP2804G [DX0001]
ZGP323HSP2808G [DX0001]
ZGP323HSP2816G [DX0001]
ZGP323HSP2832G [DX0001]
ZGP323HSP4004G [DX0001]
ZGP323HSP4008G [DX0001]
ZGP323HSP4016G [DX0001]
ZGP323HSP4032G [DX0001]
ZGP323HSS2004G@SOIC20 [DX1033]
ZGP323HSS2008G@SOIC20 [DX1033]
ZGP323HSS2016G@SOIC20 [DX1033]
ZGP323HSS2032G@SOIC20 [DX1033]
ZGP323HSS2804G@SOIC28 [DX1033]
ZGP323HSS2808G@SOIC28 [DX1033]
ZGP323HSS2816G@SOIC28 [DX1033]
ZGP323HSS2832G@SOIC28 [DX1033]
ZGP323LAH2004G@SSOP20 [DX1026]
ZGP323LAH2008G@SSOP20 [DX1026]
ZGP323LAH2016G@SSOP20 [DX1026]
ZGP323LAH2032G@SSOP20 [DX1026]
ZGP323LAH2804G@SSOP28 [DX1026]
ZGP323LAH2808G@SSOP28 [DX1026]
ZGP323LAH2816G@SSOP28 [DX1026]
ZGP323LAH2832G@SSOP28 [DX1026]
ZGP323LAH4804G@SSOP48 [DX1028]
ZGP323LAH4808G@SSOP48 [DX1028]
ZGP323LAH4816G@SSOP48 [DX1028]
ZGP323LAH4832G@SSOP48 [DX1028]
ZGP323LAP2004G [DX0001]
ZGP323LAP2008G [DX0001]
ZGP323LAP2016G [DX0001]
ZGP323LAP2032G [DX0001]
ZGP323LAP2804G [DX0001]
ZGP323LAP2808G [DX0001]
ZGP323LAP2816G [DX0001]
ZGP323LAP2832G [DX0001]
ZGP323LAP4004G [DX0001]
ZGP323LAP4008G [DX0001]
ZGP323LAP4016G [DX0001]
ZGP323LAP4032G [DX0001]
ZGP323LAS2004G@SOIC20 [DX1033]
ZGP323LAS2008G@SOIC20 [DX1033]
ZGP323LAS2016G@SOIC20 [DX1033]
ZGP323LAS2032G@SOIC20 [DX1033]
ZGP323HSP2008C [DX0001]
ZGP323HSP2016C [DX0001]
ZGP323HSP2032C [DX0001]
ZGP323HSP2804C [DX0001]
ZGP323HSP2808C [DX0001]
ZGP323HSP2816C [DX0001]
ZGP323HSP2832C [DX0001]
ZGP323HSP4004C [DX0001]
ZGP323HSP4008C [DX0001]
ZGP323HSP4016C [DX0001]
ZGP323HSP4032C [DX0001]
ZGP323HSS2004C@SOIC20 [DX1033]
ZGP323HSS2008C@SOIC20 [DX1033]
ZGP323HSS2016C@SOIC20 [DX1033]
ZGP323HSS2032C@SOIC20 [DX1033]
ZGP323HSS2804C@SOIC28 [DX1033]
ZGP323HSS2808C@SOIC28 [DX1033]
ZGP323HSS2816C@SOIC28 [DX1033]
ZGP323HSS2832C@SOIC28 [DX1033]
ZGP323LAH2004C@SSOP20 [DX1026]
ZGP323LAH2008C@SSOP20 [DX1026]
ZGP323LAH2016C@SSOP20 [DX1026]
ZGP323LAH2032C@SSOP20 [DX1026]
ZGP323LAH2804C@SSOP28 [DX1026]
ZGP323LAH2808C@SSOP28 [DX1026]
ZGP323LAH2816C@SSOP28 [DX1026]
ZGP323LAH2832C@SSOP28 [DX1026]
ZGP323LAH4804C@SSOP48 [DX1028]
ZGP323LAH4808C@SSOP48 [DX1028]
ZGP323LAH4816C@SSOP48 [DX1028]
ZGP323LAH4832C@SSOP48 [DX1028]
ZGP323LAP2004C [DX0001]
ZGP323LAP2008C [DX0001]
ZGP323LAP2016C [DX0001]
ZGP323LAP2032C [DX0001]
ZGP323LAP2804C [DX0001]
ZGP323LAP2808C [DX0001]
ZGP323LAP2816C [DX0001]
ZGP323LAP2832C [DX0001]
ZGP323LAP4004C [DX0001]
ZGP323LAP4008C [DX0001]
ZGP323LAP4016C [DX0001]
ZGP323LAP4032C [DX0001]
ZGP323LAS2004C@SOIC20 [DX1033]
ZGP323LAS2008C@SOIC20 [DX1033]
ZGP323LAS2016C@SOIC20 [DX1033]
ZGP323LAS2032C@SOIC20 [DX1033]
ZGP323LAS2804C@SOIC28 [DX1033]

ZGP323LAS2804G@SOIC28 [DX1033]
ZGP323LAS2808G@SOIC28 [DX1033]
ZGP323LAS2816G@SOIC28 [DX1033]
ZGP323LAS2832G@SOIC28 [DX1033]
ZGP323LEH2004G@SSOP20 [DX1026]
ZGP323LEH2008G@SSOP20 [DX1026]
ZGP323LEH2016G@SSOP20 [DX1026]
ZGP323LEH2032G@SSOP20 [DX1026]
ZGP323LEH2804G@SSOP28 [DX1026]
ZGP323LEH2808G@SSOP28 [DX1026]
ZGP323LEH2816G@SSOP28 [DX1026]
ZGP323LEH2832G@SSOP28 [DX1026]
ZGP323LEH4804G@SSOP48 [DX1028]
ZGP323LEH4808G@SSOP48 [DX1028]
ZGP323LEH4816G@SSOP48 [DX1028]
ZGP323LEH4832G@SSOP48 [DX1028]
ZGP323LEP2004G [DX0001]
ZGP323LEP2008G [DX0001]
ZGP323LEP2016G [DX0001]
ZGP323LEP2032G [DX0001]
ZGP323LEP2804G [DX0001]
ZGP323LEP2808G [DX0001]
ZGP323LEP2816G [DX0001]
ZGP323LEP2832G [DX0001]
ZGP323LEP4004G [DX0001]
ZGP323LEP4008G [DX0001]
ZGP323LEP4016G [DX0001]
ZGP323LEP4032G [DX0001]
ZGP323LES2004G@SOIC20 [DX1033]
ZGP323LES2008G@SOIC20 [DX1033]
ZGP323LES2016G@SOIC20 [DX1033]
ZGP323LES2032G@SOIC20 [DX1033]
ZGP323LES2804G@SOIC28 [DX1033]
ZGP323LES2808G@SOIC28 [DX1033]
ZGP323LES2816G@SOIC28 [DX1033]
ZGP323LES2832G@SOIC28 [DX1033]
ZGP323LSH2004G@SSOP20 [DX1026]
ZGP323LSH2008G@SSOP20 [DX1026]
ZGP323LSH2016G@SSOP20 [DX1026]
ZGP323LSH2032G@SSOP20 [DX1026]
ZGP323LSH2804G@SSOP28 [DX1026]
ZGP323LSH2808G@SSOP28 [DX1026]
ZGP323LSH2816G@SSOP28 [DX1026]
ZGP323LSH2832G@SSOP28 [DX1026]
ZGP323LSH4804G@SSOP48 [DX1028]
ZGP323LSH4808G@SSOP48 [DX1028]
ZGP323LSH4816G@SSOP48 [DX1028]
ZGP323LSH4832G@SSOP48 [DX1028]
ZGP323LAS2808C@SOIC28 [DX1033]
ZGP323LAS2816C@SOIC28 [DX1033]
ZGP323LAS2832C@SOIC28 [DX1033]
ZGP323LEH2004C@SSOP20 [DX1026]
ZGP323LEH2008C@SSOP20 [DX1026]
ZGP323LEH2016C@SSOP20 [DX1026]
ZGP323LEH2032C@SSOP20 [DX1026]
ZGP323LEH2804C@SSOP28 [DX1026]
ZGP323LEH2808C@SSOP28 [DX1026]
ZGP323LEH2816C@SSOP28 [DX1026]
ZGP323LEH2832C@SSOP28 [DX1026]
ZGP323LEH4804C@SSOP48 [DX1028]
ZGP323LEH4808C@SSOP48 [DX1028]
ZGP323LEH4816C@SSOP48 [DX1028]
ZGP323LEH4832C@SSOP48 [DX1028]
ZGP323LEP2004C [DX0001]
ZGP323LEP2008C [DX0001]
ZGP323LEP2016C [DX0001]
ZGP323LEP2032C [DX0001]
ZGP323LEP2804C [DX0001]
ZGP323LEP2808C [DX0001]
ZGP323LEP2816C [DX0001]
ZGP323LEP2832C [DX0001]
ZGP323LEP4004C [DX0001]
ZGP323LEP4008C [DX0001]
ZGP323LEP4016C [DX0001]
ZGP323LEP4032C [DX0001]
ZGP323LES2004C@SOIC20 [DX1033]
ZGP323LES2008C@SOIC20 [DX1033]
ZGP323LES2016C@SOIC20 [DX1033]
ZGP323LES2032C@SOIC20 [DX1033]
ZGP323LES2804C@SOIC28 [DX1033]
ZGP323LES2808C@SOIC28 [DX1033]
ZGP323LES2816C@SOIC28 [DX1033]
ZGP323LES2832C@SOIC28 [DX1033]
ZGP323LSH2004C@SSOP20 [DX1026]
ZGP323LSH2008C@SSOP20 [DX1026]
ZGP323LSH2016C@SSOP20 [DX1026]
ZGP323LSH2032C@SSOP20 [DX1026]
ZGP323LSH2804C@SSOP28 [DX1026]
ZGP323LSH2808C@SSOP28 [DX1026]
ZGP323LSH2816C@SSOP28 [DX1026]
ZGP323LSH2832C@SSOP28 [DX1026]
ZGP323LSH4804C@SSOP48 [DX1028]
ZGP323LSH4808C@SSOP48 [DX1028]
ZGP323LSH4816C@SSOP48 [DX1028]
ZGP323LSH4832C@SSOP48 [DX1028]
ZGP323LSK2032E [DX0001]

ZGP323LSK2032G [DX0001]
ZGP323LSK2832G [DX0001]
ZGP323LSK4032G [DX0001]
ZGP323LSP2004G [DX0001]
ZGP323LSP2008G [DX0001]
ZGP323LSP2016G [DX0001]
ZGP323LSP2032G [DX0001]
ZGP323LSP2804G [DX0001]
ZGP323LSP2808G [DX0001]
ZGP323LSP2816G [DX0001]
ZGP323LSP2832G [DX0001]
ZGP323LSP4004G [DX0001]
ZGP323LSP4008G [DX0001]
ZGP323LSP4016G [DX0001]
ZGP323LSP4032G [DX0001]
ZGP323LSS2004G@SOIC20 [DX1033]
ZGP323LSS2008G@SOIC20 [DX1033]
ZGP323LSS2016G@SOIC20 [DX1033]
ZGP323LSS2032G@SOIC20 [DX1033]
ZGP323LSS2804G@SOIC28 [DX1033]
ZGP323LSS2808G@SOIC28 [DX1033]
ZGP323LSS2816G@SOIC28 [DX1033]
ZGP323LSS2832G@SOIC28 [DX1033]
ZLF645E0H2064G@SSOP20 [DX1026]
ZLF645E0H2864G@SSOP28 [DX1026]
ZLF645E0P2064G [DX0001]
ZLF645E0P2864G [DX0001]
ZLF645E0Q2064G@QFN20 [DX4013]
ZLF645E0S2064G@SOIC20 [DX1033]
ZLF645E0S2864G@SOIC28 [DX1033]
ZLF645S0H2064G@SSOP20 [DX1026]
ZLF645S0H2864G@SSOP28 [DX1026]
ZLF645S0P2064G [DX0001]
ZLF645S0P2864G [DX0001]
ZLF645S0Q2064G@QFN20 [DX4013]
ZLF645S0S2064G@SOIC20 [DX1033]
ZLF645S0S2864G@SOIC28 [DX1033]
ZLP12840H2028G@SSOP20 [DX1026]
ZLP12840H2032G@SSOP20 [DX1026]
ZLP12840H2064G@SSOP20 [DX1026]
ZLP12840H2096G@SSOP20 [DX1026]
ZLP12840H2828G@SSOP28 [DX1026]
ZLP12840H2832G@SSOP28 [DX1026]
ZLP12840H2864G@SSOP28 [DX1026]
ZLP12840H2896G@SSOP28 [DX1026]
ZLP12840P2028G [DX0001]
ZLP12840P2032G [DX0001]
ZLP12840P2064G [DX0001]
ZGP323LSK2832E [DX0001]
ZGP323LSK4032E [DX0001]
ZGP323LSP2004C [DX0001]
ZGP323LSP2008C [DX0001]
ZGP323LSP2016C [DX0001]
ZGP323LSP2032C [DX0001]
ZGP323LSP2804C [DX0001]
ZGP323LSP2808C [DX0001]
ZGP323LSP2816C [DX0001]
ZGP323LSP2832C [DX0001]
ZGP323LSP4004C [DX0001]
ZGP323LSP4008C [DX0001]
ZGP323LSP4016C [DX0001]
ZGP323LSP4032C [DX0001]
ZGP323LSS2004C@SOIC20 [DX1033]
ZGP323LSS2008C@SOIC20 [DX1033]
ZGP323LSS2016C@SOIC20 [DX1033]
ZGP323LSS2032C@SOIC20 [DX1033]
ZGP323LSS2804C@SOIC28 [DX1033]
ZGP323LSS2808C@SOIC28 [DX1033]
ZGP323LSS2816C@SOIC28 [DX1033]
ZGP323LSS2832C@SOIC28 [DX1033]
ZLF645E0H2032G@SSOP20 [DX1026]
ZLF645E0H2832G@SSOP28 [DX1026]
ZLF645E0P2032G [DX0001]
ZLF645E0P2832G [DX0001]
ZLF645E0Q2032G@QFN20 [DX4013]
ZLF645E0S2032G@SOIC20 [DX1033]
ZLF645E0S2832G@SOIC28 [DX1033]
ZLF645S0H2032G@SSOP20 [DX1026]
ZLF645S0H2832G@SSOP28 [DX1026]
ZLF645S0P2032G [DX0001]
ZLF645S0P2832G [DX0001]
ZLF645S0Q2032G@QFN20 [DX4013]
ZLF645S0S2032G@SOIC20 [DX1033]
ZLF645S0S2832G@SOIC28 [DX1033]
ZLP12840H2028C@SSOP20 [DX1026]
ZLP12840H2032C@SSOP20 [DX1026]
ZLP12840H2064C@SSOP20 [DX1026]
ZLP12840H2096C@SSOP20 [DX1026]
ZLP12840H2828C@SSOP28 [DX1026]
ZLP12840H2832C@SSOP28 [DX1026]
ZLP12840H2864C@SSOP28 [DX1026]
ZLP12840H2896C@SSOP28 [DX1026]
ZLP12840P2028C [DX0001]
ZLP12840P2032C [DX0001]
ZLP12840P2064C [DX0001]
ZLP12840P2096C [DX0001]

ZLP12840P2096G [DX0001]
ZLP12840P2828G [DX0001]
ZLP12840P2832G [DX0001]
ZLP12840P2864G [DX0001]
ZLP12840P2896G [DX0001]
ZLP12840S2028G@SOIC20 [DX1033]
ZLP12840S2032G@SOIC20 [DX1033]
ZLP12840S2064G@SOIC20 [DX1033]
ZLP12840S2096G@SOIC20 [DX1033]
ZLP12840S2828G@SOIC28 [DX1033]
ZLP12840S2832G@SOIC28 [DX1033]
ZLP12840S2864G@SOIC28 [DX1033]
ZLP12840S2896G@SOIC28 [DX1033]
ZLP32300H2004G@SSOP20 [DX1026]
ZLP32300H2008G@SSOP20 [DX1026]
ZLP32300H2016G@SSOP20 [DX1026]
ZLP32300H2032G@SSOP20 [DX1026]
ZLP32300H2804G@SSOP28 [DX1026]
ZLP32300H2808G@SSOP28 [DX1026]
ZLP32300H2816G@SSOP28 [DX1026]
ZLP32300H2832G@SSOP28 [DX1026]
ZLP32300H4804G@SSOP48 [DX1028]
ZLP32300H4808G@SSOP48 [DX1028]
ZLP32300H4816G@SSOP48 [DX1028]
ZLP32300H4832G@SSOP48 [DX1028]
ZLP32300P2004G [DX0001]
ZLP32300P2008G [DX0001]
ZLP32300P2016G [DX0001]
ZLP32300P2032G [DX0001]
ZLP32300P2804G [DX0001]
ZLP32300P2808G [DX0001]
ZLP32300P2816G [DX0001]
ZLP32300P2832G [DX0001]
ZLP32300P4004G [DX0001]
ZLP32300P4008G [DX0001]
ZLP32300P4016G [DX0001]
ZLP32300P4032G [DX0001]
ZLP32300S2004G@SOIC20 [DX1033]
ZLP32300S2008G@SOIC20 [DX1033]
ZLP32300S2016G@SOIC20 [DX1033]
ZLP32300S2032G@SOIC20 [DX1033]
ZLP32300S2804G@SOIC28 [DX1033]
ZLP32300S2808G@SOIC28 [DX1033]
ZLP32300S2816G@SOIC28 [DX1033]
ZLP32300S2832G@SOIC28 [DX1033]
ZLP12840P2828C [DX0001]
ZLP12840P2832C [DX0001]
ZLP12840P2864C [DX0001]
ZLP12840P2896C [DX0001]
ZLP12840S2028C@SOIC20 [DX1033]
ZLP12840S2032C@SOIC20 [DX1033]
ZLP12840S2064C@SOIC20 [DX1033]
ZLP12840S2096C@SOIC20 [DX1033]
ZLP12840S2828C@SOIC28 [DX1033]
ZLP12840S2832C@SOIC28 [DX1033]
ZLP12840S2864C@SOIC28 [DX1033]
ZLP12840S2896C@SOIC28 [DX1033]
ZLP32300H2004C@SSOP20 [DX1026]
ZLP32300H2008C@SSOP20 [DX1026]
ZLP32300H2016C@SSOP20 [DX1026]
ZLP32300H2032C@SSOP20 [DX1026]
ZLP32300H2804C@SSOP28 [DX1026]
ZLP32300H2808C@SSOP28 [DX1026]
ZLP32300H2816C@SSOP28 [DX1026]
ZLP32300H2832C@SSOP28 [DX1026]
ZLP32300H4804C@SSOP48 [DX1028]
ZLP32300H4808C@SSOP48 [DX1028]
ZLP32300H4816C@SSOP48 [DX1028]
ZLP32300H4832C@SSOP48 [DX1028]
ZLP32300P2004C [DX0001]
ZLP32300P2008C [DX0001]
ZLP32300P2016C [DX0001]
ZLP32300P2032C [DX0001]
ZLP32300P2804C [DX0001]
ZLP32300P2808C [DX0001]
ZLP32300P2816C [DX0001]
ZLP32300P2832C [DX0001]
ZLP32300P4004C [DX0001]
ZLP32300P4008C [DX0001]
ZLP32300P4016C [DX0001]
ZLP32300P4032C [DX0001]
ZLP32300S2004C@SOIC20 [DX1033]
ZLP32300S2008C@SOIC20 [DX1033]
ZLP32300S2016C@SOIC20 [DX1033]
ZLP32300S2032C@SOIC20 [DX1033]
ZLP32300S2804C@SOIC28 [DX1033]
ZLP32300S2808C@SOIC28 [DX1033]
ZLP32300S2816C@SOIC28 [DX1033]
ZLP32300S2832C@SOIC28 [DX1033]

E(E)PROM/FRAM/NVRAM

U62256 [DX0001]
U6264 [DX0001]
U6264@SOIC28
U6264A [DX0001]
U6264A@SOIC28 [DX1035]
U62H256A@SOIC28 [DX1035]
U62H256S@SOIC28 [DX1035]
U62H64SA@SOIC28 [DX1033]
U630H16 [DX0001]
U630H16@SOIC28 [DX1035]
U630H64 [DX0001]
U630H64@SOIC28 [DX1035]
U631H16 [DX0001]
U631H16@SOIC24 [DX1033]
U631H16@SOIC28 [DX1035]
U631H256 [DX0001]
U631H256@SOIC28 [DX1035]
U631H64 [DX0001]
U631H64@SOIC28 [DX1035]
U632H16 [DX0001]
U632H16@SOIC28 [DX1035]
U632H64 [DX0001]
U632H64@SOIC28 [DX1035]
U634H256 [DX0001]
U634H256@SOIC32 [DX1035]
U635H16 [DX0001]
U635H16@SOIC24 [DX1033]
U635H256 [DX0001]
U635H256@SOIC28 [DX1035]
U635H64 [DX0001]
U635H64@SOIC28 [DX1035]
U63716 [DX0001]
U637256 [DX0001]
U63764 [DX0001]
U637H256 [DX0001]
UL62H256A@SOIC28 [DX1035]
UL631H256@SOIC28 [DX1035]
UL631H256@TSOP32 [DX1002]
UL634H256@SOIC32 [DX1035]
UL634H256@TSOP32 [DX1002]
UL635H256@SOIC28 [DX1035]
UL635H256@SOIC32 [DX1002]

ZOWEE

E(E)PROM/FRAM/NVRAM

MX29GL256EHT2 [DX1011]