Interface module - UM-25 FLK26/FRONT/Q - 2959528

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(http://phoenixcontact.com/download)

VARIOFACE SLIM LINE, with screw connection and flat-ribbon cable connector, for assembly at a right angle on NS 35/7.5, 26 positions

The illustration shows a 20-position version

Key commercial data

Packing unit	1 pc
GTIN	4 017918 086176
Weight per Piece (excluding packing)	153.95 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	25 mm
Height	217 mm
Depth	45 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C

General

Max. permissible operating voltage	< 50 V AC
	60 V DC
Max. perm. current (per branch)	0.8 A (data valid for 100% coincidence factor)
Number of positions	26
Mounting position	any

Interface module - UM-25 FLK26/FRONT/Q - 2959528

Technical data

General

Degree of protection	IP00
Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (Functional insulation)
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	4 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	2.5 mm²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	Flat-ribbon cable connection
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	26

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604

Interface module - UM-25 FLK26/FRONT/Q - 2959528

Classifications

ETIM

ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

System cable

Cable - FLK 26/EZ-DR/ 50/KONFEK - 2299385

Round cable set, with two 26-pos. socket strips, (1:1 connection), cable length: 0.5 m

Interface module - UM-25 FLK26/FRONT/Q - 2959528

Accessories

Cable - FLK 26/EZ-DR/ 100/KONFEK - 2299398

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 1 m

---

Cable - FLK 26/EZ-DR/ 150/KONFEK - 2299408

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 1.5 m

---

Cable - FLK 26/EZ-DR/ 300/KONFEK - 2299424

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 3 m

---

Cable - FLK 26/EZ-DR/ 400/KONFEK - 2299437

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 4 m

---

Cable - FLK 26/EZ-DR/ 600/KONFEK - 2299440

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 6 m

---

Interface module - UM-25 FLK26/FRONT/Q - 2959528

Accessories

Cable - FLK 26/EZ-DR/ 800/KONFEK - 2299453

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 8 m

---

Cable - FLK 26/EZ-DR/1000/KONFEK - 2299466

Round cable set, with two 26-pos. socket strips (1:1 connection), cable length: 10 m

---

Cable - FLK EZ-DR.../.../... - 2295059

Round cable, with preassembly, not shielded, variable cable length

---

Phoenix Contact 2015 © - all rights reserved
http://www.phoenixcontact.com