Part Number: 0010633024

Status: Active

Description: 5.00mm (.197") Pitch SPOX™ Crimp Housing, Female, With Friction Ramp and Void, 2 Circuits



Series

image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification PS-5199-001 (PDF)
Product Specification PS-5199-002 (PDF)
Product Specification PS-5199-003 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
TUV	R72090224
UL	E29179

General

Product Family	Crimp Housings
Series	5199
Application	Signal, Wire-to-Board
Product Name	SPOX™

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm (.197")
Stackable	Yes
Temperature Range - Operating	-40°C to +105°C

Material Info

Old Part Number	5199-02

Reference - Drawing Numbers

Product Specification	PS-5199-001, PS-5199-002, PS-5199-003, RPS-5199-001, RPS-5289-002
Sales Drawing	SD-5199-001

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
5199Series

Mates With
5287 , 5288 , 5289 , 53331

Use With
5194 , 5225