



CorePro LEDbulb

CorePro LEDBulb 9.5-60W B22 830

Delivering a warm, halogen-like accent beam, LEDspots are a perfect fit for spot lighting and have a broad compatibility with transformers. LEDspots are compatible with most existing fixtures with a GU10 / MR16 GU5.3 / E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs. LEDcandle and LEDluster are compatible with existing fixtures with an E27/E14 holder and are designed for retrofit replacement of incandescent lamps. LEDlamps deliver huge energy savings and minimize maintenance cost.



PHILIPS

Product data

• General Characteristics

Cap-Base	BC
Bulb	A60 [A 60mm]
Rated Lifetime	15000 hr
Nominal Lifetime hours	15000 hr

• Light Technical Characteristics

Colour Code	830
Colour Designation	White
Correlated Colour Temperature	3000 K
Luminous Flux	806 Lm
Colour rendering index	80
Luminous Efficacy Lamp	80.60 Lm/W
Colour Temperature	3000 K [CCT 3000K]
Rated Luminous Flux	806 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	6 steps

• Electrical Characteristics

Wattage	9.5 W
Voltage	220-240 V
Line Frequency	50-60 Hz
Power Factor	0.7 -
Lamp Current mA	57 mA
Dimmable	No
Wattage Equivalent	60 W
Rated Wattage	9.5 W
Starting Time	0.5 s
Suitable for accent lighting	No

• Temperature Characteristics

• Environmental characteristics

Energy Efficiency Label (EEL)	A+
-------------------------------	----

• Measuring Conditions

Switching cycle	50000X
-----------------	--------


• Product Dimensions

Overall Length C	101.1 mm
Diameter D	56.2 mm

• Product Data

Order code	754602 00
Full product code	871829175460200
Full product name	CorePro LEDBulb 9.5-60W B22 830
Order product name	CorePro LEDBulb 9.5-60W B22 830
Pieces per pack	1
Packing configuration	6
Packs per outerbox	6
Bar code on pack - EAN1	8718291754602
Bar code on outerbox - EAN3	8718291754619
Logistic code(s) - 12NC	929000249232
Net weight per piece	0.081 kg


Dimensional drawing




CorePro LEDBulb 9.5-60W B22 830

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED 9.5-60W B22 830 220-240V	101.1	-	56.2	-

Dimensional drawing



Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, July 15
data subject to change