REVERSE MOUNT, NON-LOCKING & EDGE LOCKING CIRCUIT BOARD SUPPORTS

RCBSR
Reverse Mounted Non-Locking Support



Snap-Lock: .125 (3.2)
Panel Thickness: .062 (1.6)

Snap-Lock: .187 (4.8)
Panel Thickness: .059–.063 (1.5–1.6)

Item No.	A In	A mm	Bulk Pack Qty.
RCBSR-4-01	0.250	6.4	1000
RCBSR-5-01	0.313	7.9	1000
RCBSR-6-01	0.375	9.5	1000
RCBSR-7-01	0.438	11.1	1000

Item No.	A In	A mm	Bulk Pack Qty.
RCBSR-8-01	0.500	12.7	1000
RCBSR-9-01	0.563	14.3	1000
RCBSR-10-01	0.625	15.9	1000

CRCBSRE
Reverse Mount Non-Locking Support



New



Top Hole: Snap-fit: .156 (4)
Panel Thickness: .062 (1.6)

Bottom Hole: Snap-lock: .213 (5.4)
Panel Thickness: .047 - .079 (1.2 - 2.0)

- Inserts into both holes from chassis underside
- Thin buttonhead for minimal protrusion under chassis
- Cupped head provides for tight holding in chassis
- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	"A" Standoff Height	Bulk Pack Qty.
CRCBSRE-3-01	3/16 (4.8)	1000
CRCBSRE-4-01	1/4 (6.4)	1000
CRCBSRE-6-01	3/8 (9.5)	1000
CRCBSRE-8-01	1/2 (12.7)	1000
CRCBSRE-10-01	5/8 (15.9)	1000

EHCBS
Edge Holding Circuit Board Support





Top Board Hole Location



Top Hole: Fit: .156 (4)
Panel Thickness: .062 (1.57)

Bottom Hole: Snap-lock: .187 (4.75)
Panel Thickness: .031 - .078 (1.79 - 1.98)

Item No. "B" = .60 (15.2) "C" = .29 (7.5)	Item No. "B" = .24 (6.1) "C" = .24 (6.1)	Item No. "B" = .24 (6.1) "C" = .29 (7.5)	"A" Standoff Height	Bulk Pack Qty.
EHCBS-5-01	EHCBS-6-5-01	EHCBS-7-5-01	5/16 (7.9)	1000
EHCBS-6-01	EHCBS-6-6-01	EHCBS-7-6-01	3/8 (9.5)	1000
EHCBS-8-01	EHCBS-6-8-01	EHCBS-7-8-01	1/2 (12.7)	1000
EHCBS-10-01	EHCBS-6-10-01	EHCBS-7-10-01	5/8 (15.9)	1000
EHCBS-12-01	EHCBS-6-12-01	EHCBS-7-12-01	3/4 (19.1)	1000
EHCBS-14-01	EHCBS-6-14-01	EHCBS-7-14-01	7/8 (22.2)	1000
EHCBS-16-01	EHCBS-6-16-01	EHCBS-7-16-01	1 (25.4)	1000

- Long nose facilitates alignment of components on board with the mating parts on the chassis
- PCB is easy to remove for service
- Material: UL94 V-2 Nylon 6/6
- Color: Natural



Mounting Hole. To Fit Hole: .187 (4.8)
Panel Thickness: .019 - .078 (0.5 - 2.0)

PCB Thickness: .062–.070 (1.6–1.8)

Item No.	A In	A mm	Bulk Pack Qty.
CBEHS005A	0.250	6.4	1000

TEHCBS Series
Edge Holding Support



Top Hole: .156 (4.0)
Panel Thickness: .062 (1.6)

Bottom Hole: For Metal #6 Self-Tapping Screw

Specifications:
- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2

Item No.	A In	A mm	B In	B mm	Bulk Pack Qty.
TEHCBS-4-01	0.250	6.4	0.250	6.4	1000
TEHCBS-5-01	0.313	7.9	0.200	5.1	1000
TEHCBS-6-01	0.375	9.5	0.250	6.4	1000
TEHCBS-8-01	0.500	12.7	0.250	6.4	1000
TEHCBS-10-01	0.625	15.9	0.250	6.4	1000
TEHCBS-12-01	0.750	19.1	0.250	6.4	1000
TEHCBS-14-01	0.875	22.2	0.250	6.4	1000
TEHCBS-16-01	1.000	25.4	0.250	6.4	1000

Pages 0672 - 0681.indd 675 11/6/2013 4:20:11 PM