ENGLISH

Datasheet

RS Pro Xenon V10994 Series Beacon, Flashing, Surface Mount, 10 → 30 V dc

RS Stock No: **235-483**

Product Details

RS Pro 14 W xenon flashing beacon offers high performance that is suitable for 12/24 V dc applications requiring maximum visibility. This single or double flash xenon flashing beacon is perfect for commercial, fleet or utility vehicles. It features vibration protected circuits, reverse polarity and IP56 degree of protection. The beacon has a large cage guard that is suitable for three-point mounting.

Features and Benefits

- Vibration protected circuits
- Reverse polarity protection
- Supply voltage: 12/24 V dc
- Current consumption: 2/1 A at 12/24 V
- Single or double flash operation possible
- Flash rate: 125 fpm
- IP56 rated
- Operating temperature range: -30 to +50°C
- Magnetic versions are rated to 70 mph

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH

Specifications:

Bulb Type	Xenon
Current Type	DC
Housing Colour	Black
Lamp Included	Yes
Lens Colour	Lens Not Included
Light Effect	Flashing
Special Features	Vibration, Reverse Polarity Protected
Standards Met	EMC (ECE R10); RoHS Compliant
Base Diameter	130 mm
Current Consumption	2/1 A
Height	228 mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C
IP Rating	IP56
Mounting Style	DIN Rail
Supply Voltage	10 to 30 V dc
Flash Rate	125 fp/min

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.