

# M 238-V0



Euromas  
Enclosures, polycarbonate V0

**Order no.: 02238094**

**Colour of enclosure group**

Light grey, similar to RAL 7035; special colours on request

**Protection class**


Depending on the model: IP 65 or IP 66/DIN EN 60529; IP 67 available on request for some sizes.

**Enclosure material**

ABS, PC (UV stabilised) and selected sizes in PC UL 94 V0 (additional UL 94 V0 versions on request), seal made of CR; for details see Technical Information

Scope of delivery: Lid and base, lid screws made of V2A, self-tapping screws for mounting bosses

Note: V0 = version in UL 94 V0 enclosure material.  
IP = Ingress protection acc. to DIN EN 60529



<b>A</b>	160 mm
<b>B</b>	120 mm
<b>C</b>	90 mm
<b>a1</b>	153 mm
<b>a2</b>	134,2 mm
<b>b1</b>	113 mm
<b>b2</b>	74,2 mm
<b>c1</b>	30 mm
<b>c2</b>	83,5 mm

**Technical drawings**

3D product data in STEP format:

[Registration necessary](#)

Basic drawing for processing work:

[02238094\\_M-238-V0-G.dxf](#) (325 KB)

Catalogue drawing in PDF format:

[02238094\\_M-238-V0.pdf](#) (92 KB)

**Chapter download**

[Euromas ABS PC GB.pdf](#) (338 KB)

## Accessories



**Mounting plates, laminated paper (Pertinax), galvanised steel for version 260**

22001100

[M](#)

For EM/ET 238, M/T 238, M/T 246



**Rubber feet, plug-in**

22003300

[E](#)

For M/T 208-260



**Silicone seal for lid**

22004300

[SIL](#)

For M/T 238, M/T 246



**Wall brackets on rear, screw-on, polycarbonate**

22004900

[WL](#)

For M/T 210-243, M/T 246-253



**DIN rails DIN EN 60715 TH 15**

22002000

[TS 15](#)

For M/T 219-220, M/T 231-235, M/T 238, M/T 246, P 325, M/T 2381



**DIN rails DIN EN 60715 G 32**

22002010

[TS 32](#)

For M/T 219-220, M/T 231-235, M/T 238, M/T 246, P 316, P 325, M/T 2381



**DIN rails DIN EN 60715 TH 35**

22002020

[TS 35](#)

For M/T 219-220, M/T 231-235, M/T 238, M/T 246, P



**Threaded inserts for mounting bosses**



59002810 [DODGE M3x6,5](#) ND = 4.0 x 6.5  
59002820 [DODGE M4x9,5](#) ND = 5.4 x 9.5



**Set of hinges**

22006000 [SchM](#)

\* = Available on request