ENGLISH

Datasheet

RS 9 Core Screened Industrial Cable, PVC Sheath, 4.2mm OD, 0.055 mm² CSA 0.25 A, 300 V, 25m

Stock Number – 660-0404

Description:
Rated Temperature (oC): -20 ~ 80
Rated Voltage (V):300
Flammability Test: IEC60332-1

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH

Construction:
Conductor: Tinned Copper
Conductor Dia. (mm): 0.10±0.008 x 7
Insulation: PVC
Insulation Dia. (mm): 0.7±0.05 x 9C
Filler:1.3 PVC Strip
Tape: Mylar Spiral
Coverage:≥115%
Braid Shield : Tinned Copper
Conductor Dia. (mm): 0.10
Conductor Qty: 16x8
Pitch(mm):
Coverage : 91%
ID Thread： Green, White/Green
A rip cord : 210 D
Jacket: FR-PVC
Outer Dia. (mm): 4.2±0.1

Colour:
The colour of the insulation: Red , Blue , Green ,
Yellow ,
White , Black , Brown , Violet , Orange
The jacket colour: Black
Marking(3times/m):
RS 6600404 7 - 1 - 9C

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH

Electrical Characteristics:
Max.Conductor DC Resistance at 20℃（Ω/Km）:
<345
Min.Insulation DC Resistance at 20℃（MΩ*KM）:
>200
Current Rating : 0.25 A



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.