THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
—	—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECO-11-004835	11MAR11	RK	HMR







T&B PART NO (REF)	A	NO OF POSN	PART NO
609-6431HD	85.95	(3.384)	64	1-1437022-3
609-5031HD	68.17	(2.684)	50	8-1437021-1
609-4031HD	55.47	(2.184)	40	5-1437021-5
609-3431HD	47.85	(1.884)	34	3-1437021-2
609-2631HD	37.69	(1.484)	26	1-1437021-2
609-2031HD	30.07	(1.184)	20	8-1437020-6
609-1631HD	24.99	(0.984)	16	6-1437020-6
609-1431HD	22.45	(0.884)	14	5-1437020-1
609-1031HD	17.37	(0.684)	10	3-1437020-7

MATERIAL: GLASS REINFORCED THERMOPLASTIC RATED 94V-0.

2. COLOR: BLUE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL 1

FINISH -

DWN W.DABULAS 3/25/83
CHK G.KLEMM 3/25/83
APVD R.R. 3/31/83
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME HEAVY DUTY STRAIN RELIEF FEMALE SOCKET CONNECTOR -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-3-1437020-7	—

CUSTOMER DRAWING

SCALE	SHEET	REV
10:1	1 OF 1	B1