ENGLISH

Datasheet

RS Pro 50Ω Straight Cable Mount MMCX Connector, jack, Solder Termination, 0 to 6GHz

RS Stock No: **656-0154**

Product Details

RS Pro cable mount MMCX connector jack is suitable for operating frequencies ranging from 0 - 6 GHz. It is designed for 50 Ω impedance applications. This straight connector jack offers solder termination and includes gold plated copper body and contacts for superior connectivity. The snap on mechanism gives flexibility in PCB layouts by allowing for 360° rotation.

Features and Benefits

- DC to 6GHz frequency range
- Available in cable, panel and PCB mount versions
- Low RF leakage

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH

Specifications:

Body Orientation	Straight
Body Plating	Gold
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 6 GHz
Size	Micro Miniature
Termination Method	Solder
Dimensions	8.5 x 5 mm

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.