THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	RELEASED PER EC 0513-0209-03	02 JAN 04	LB	SB





1. CONNECTOR ACCEPTS 22 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
2. FLAME RETARDANT 94V-0 RATED GLASS FILLED NYLON, COLOR: BLACK.
3. CARBON STEEL.
4. .000200 MIN. TIN PLATE OVER .000100 MIN. COPPER UNDERPLATE.

1658685-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCH

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±.005
4 PLC ±-
ANGLES ±2°

MATERIAL
MOLDED PARTS: 2
SHELLS: 3

FINISH
SHELLS: 4

DWN	L. BAUM	02JAN04
CHK	S. BOLASH	02JAN04
APVD	M. WALMSLEY	02JAN04
PRODUCT SPEC	108-1268	
APPLICATION SPEC	114-10001	
WEIGHT	–	

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
RECEPTACLE ASSEMBLY, SIZE 5, 78 POSN, HDP-22, AMPLIMITE®

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C- 1658685	–

SCALE	SHEET	OF	REV
3:1	1	1	0

AMP 1471-9 REV 11JUN97

17-FEB-04 11:36:50 b8420 /nd/walmsley/job8