Lamps with metal bases for cars

Product benefits

- Wide product range
- Reliable quality

Product features

- Original spare parts

© 2015, OSRAM GmbH. All rights reserved.



Product line drawing



Product line drawing



Product line drawing



Product line drawing



Product line drawing



Product line drawing



Product line drawing

© 2015, OSRAM GmbH. All rights reserved.

Technical data

	Electrical data					Photometrical data		Dimensions & weight
Product description	**Power input**	**Nominal wattage**	**Nominal voltage**	**Power input tolerance**	**Test voltage**	**Luminous flux**	**Luminous flux tolerance**	**Length**
64136	25 W	21.0 W	12.0 V	±5 %	13.5 V	600 lm	±12 %	38.9 mm
64132	7 W	6.00 W	12.0 V	±5 %	13.5 V	125 lm	±12 %	33.0 mm
7225	25 / 5 W		12.0 V	±6 / ±10 %	13.5 / 13.5 V	440/15 lm	±15 / ±20 %	52.0 mm
7528	25 / 6 W		12.0 V	±6 / ±10 %	13.5 / 13.5 V	440/35 lm	±15 / ±20 %	52.5 mm
7506	25 W	21.0 W	12.0 V	±6 %	13.5 V	460 lm	±15 %	52.5 mm
7507 [1)]	25 W	21.0 W	12.0 V	±6 %	13.5 V	280 lm	±20 %	52.6 mm
5008	10 W	10.0 W	12.0 V	±10 %	13.5 V	125 lm	±20 %	37.5 mm
5007	5 W	5.00 W	12.0 V	±10 %	13.5 V	50 lm	±20 %	37.5 mm
5009 [1)]	10 W	10.0 W	12.0 V	±10 %	13.5 V	75 lm	±20 %	37.5 mm
3893	4 W	4.00 W	12.0 V	±10 %	13.5 V	35 lm	±20 %	27.4 mm
3796	2 W	2.00 W	12.0 V	±8 %	13.5 V	12.5 lm	±25 %	23.9 mm
3860	5 W	5.00 W	12.0 V	±15 %	13.5 V	50 lm	±20 %	27.4 mm
7240	25 / 6 W		12.0 V	±6 / ±10 %	13.5 V	440/35 lm	±15 / ±20 %	52.5 mm

		Lifespan		Additional product data	Certificates & standards	Country specific categorizations
Product description	**Diameter**	**Lifespan B3**	**Lifespan Tc**	**Base (standard designation)**	**ECE category**	**Order reference**
64136	9 mm	300 h	600 h	BAY9s	H21W	64136 21W 12V B
64132	9 mm	350 h	700 h	BAX9s	H6W	64132 6W 12V BA
7225	25.0 mm	180 / 1250 h [2)]	290 / 4000 h [2)]	BAZ15d	P21/4W	7225 21/4W 12V
7528	26.5 mm	180 / 1250 h [2)]	290 / 4000 h [2)]	BAY15d	P21/5W	7528 21/5W 12V
7506	26.5 mm	250 h	500 h	BA15s	P21W	7506 21W 12V BA
7507 [1)]	25.0 mm	250 h	500 h	BAU15s	PY21W	7507 21W 12V BA

© 2015, OSRAM GmbH. All rights reserved.

		Lifespan		Additional product data	Certificates & standards	Country specific categorizations
Product description	**Diameter**	**Lifespan B3**	**Lifespan Tc**	**Base (standard designation)**	**ECE category**	**Order reference**
5008	19.0 mm	350 h	800 h	BA15s	R10W	5008 10W 12V BA
5007	16.0 mm	350 h	800 h	BA15s	R5W	5007 5W 12V BA1
5009 [1]	16.0 mm	350 h	800 h	BAU15s	RY10W	5009 10W 12V BA
3893	8.8 mm	600 h	1200 h	BA9s	T4W	3893 4W 12V BA9
3796	9 mm	300 h	750 h	BA9s	-	3796 2W 12V BA9
3860	9 mm	400 h	1000 h	BA9s	-	3860 5W 12V BA9
7240	25.0 mm	180 / 1250 h	290 / 4000 h	BA15d	-	7240 21/5W 12V

[1] Amber lamp for clear indicators

[2] Filament 1

© 2015, OSRAM GmbH. All rights reserved.

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

© 2015, OSRAM GmbH. All rights reserved.