0 600 910 470 – GHP 5-55

Material number	0 600 910 470
EAN	3165140794503
Adjustable 3-in-1 lance (stainless steel)	✓
Bosch gun	✓
Voltage 240 V	✓
Packaging dimensions (width x length x height)	440 x 786 x 398 mm
Voltage, electrical	240 V

Technical data

Technical data

Max. pressure	130 bar
Rated input power	2.200 W
Operating pressure	115 bar
Max. inlet temperature	50 °C
Cable length	5 m
Hose length	8 m
Material (hose)	Reinforced rubber hose
Weight (without accessories)	19 kg
Rated flow rate	500 l/h
Max. flow rate	520 l/h
Pump system	Wobble plate
Pistons	Steel
Motor type	Induction
Lance	Adjustable 3-in-1 lance (stainless steel)

Noise/vibration information

Sound pressure level	78 dB(A)
Sound power level	92 dB(A)
Uncertainty K	2.5 dB

Sales information

Positioning

- Powerful and versatile: A compact and mobile all-rounder for daily use

User benefit

- Compact: Easy manoeuvrability and storage due to metal telescopic handle and large rubber wheels
- Convenient: Ready to use out of the box. Practical storage options for lance and nozzles even during ongoing work
- Versatile: Used both in horizontal and vertical positions. Self-priming, meaning it can draw water from a pressureless water source