




Specially designed wrench removes and installs hard-to-reach oil filters



Mostly used in measuring the clearance between two parts



Two-way action installs or removes filters

Tools that have been specially designed to your greatest conveniences:

- Simplify your job
- Easy to use
- Reliable and Safe to use



**6PC. AUTO BODY REPAIR KIT**

PART NO.	CONTENT			G.W.(kg)
09152	6PC.	4		15.2

DESCRIPTION:  
 1 - Anvil Dolly  
 1 - Curved Dolly  
 1 - Pry & Bumping Spoon  
 1 - Toe Dolly  
 1 - Light Shrinking Hammer  
 1 - Pick & Finishing Hammer



**14PC. FEELER GAUGES SET**

PART NO.	CONTENT			G.W.(kg)
09401	14PC.	12	48	13.0

DESCRIPTION:  
 0.05mm, 0.10mm, 0.15mm,  
 0.20mm, 0.25mm, 0.30mm,  
 0.40mm, 0.50mm, 0.60mm,  
 0.70mm, 0.80mm, 0.90mm,  
 1.00mm



Blade Length: 3"

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

Conform to DIN2275 & JIS B 7524-1992 standard.

**16PC. FEELER GAUGES SET**

PART NO.	CONTENT			G.W.(kg)
09402	16PC.	12	48	18.0

DESCRIPTION:  
 0.05mm, 0.10mm, 0.15mm,  
 0.20mm, 0.25mm, 0.30mm,  
 0.35mm, 0.40mm, 0.50mm,  
 0.55mm, 0.60mm, 0.70mm,  
 0.75mm, 0.80mm, 0.90mm,  
 1.00mm



Blade Length: 4"

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

Conform to DIN2275 & JIS B 7524-1992 standard.

**23PC. FEELER GAUGES SET**

PART NO.	CONTENT			G.W.(kg)
09405	23PC.	12	48	14.0

DESCRIPTION:  
 0.02mm, 0.03mm, 0.04mm,  
 0.05mm, 0.10mm, 0.15mm,  
 0.20mm, 0.25mm, 0.30mm,  
 0.35mm, 0.40mm, 0.45mm,  
 0.50mm, 0.55mm, 0.60mm,  
 0.65mm, 0.70mm, 0.75mm,  
 0.80mm, 0.85mm, 0.90mm,  
 0.95mm, 1.00mm



Blade Length: 4"


⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

Conform to DIN2275 & JIS B 7524-1992 standard.

**32PC. FEELER GAUGES SET**

PART NO.	CONTENT			G.W.(kg)
09407	32PC.	12	48	22.0

DESCRIPTION:  
 0.02mm, 0.03mm, 0.04mm,  
 0.05mm, 0.06mm, 0.07mm,  
 0.08mm, 0.09mm, 0.10mm,  
 0.13mm, 0.15mm, 0.18mm,  
 0.20mm, 0.23mm, 0.25mm,  
 0.28mm, 0.30mm, 0.33mm,  
 0.38mm, 0.40mm, 0.45mm,  
 0.50mm, 0.55mm, 0.60mm,  
 0.63mm, 0.65mm, 0.70mm,  
 0.75mm, 0.80mm, 0.85mm,  
 0.90mm, 1.00mm



Blade Length: 4"

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

Conform to DIN2275 & JIS B 7524-1992 standard.

**8PC. END CAP OIL FILTER WRENCH SET**

PART NO.	CONTENT			G.W.(kg)
09703	8PC.	2	4	9.1

DESCRIPTION:  
 6 - 3/8"DR. End Cap Oil Filter Wrench  
 65, 74/76, 76, 80, 90, 93mm  
 1 - 3/8"DR. Quick-Release Ratchet  
 1 - 1/2"DR. Adapter 3/8"DR.



● Specially designed wrench removes and installs hard-to-reach oil filters. Caution: Do not use with power tools.