Datasheet

Product Name:	UL1213 26AWG
Product Discription:	UL1213 26AWG
Specification No.:	
Customer's Name:	

Description

Rated Voltage:	Not specified
Rated Temperature:	105℃, 60 ℃ Oil
Reference Standard:	UL758

Cross Section



Marking

No marking on the cable jacket, have UL label on the Reel.

Applications

Internal wiring where not subjected to mechanical abuse, Oil Resistant 60 deg C.

Revisions

Version	Description	Drawn by	Approved by	Date
0	New document issue	Danniel	Jason	24/04/2015

Construction

Conductor	**Stranded Sliver plated copper**		
Size(AWG)	26		
Construction(±0.008mm)	7/0.16		
Stranded Dia.(mm)Ref.	0.48		
Insulation Material	PTFE		
Insulation Color	ANY COLOR		
Ave Thickness(mm)	0.2		
Insulation Dia.(±0.08mm)	0.97		

Remark:

8739661 Red	8739664 Blue	8739683 Grey	8739686 Violet
8739658 Black	8739668 White	8739670 Yellow	
8739652 Brown	8739677 Green	8739674 Orange	

Characteristics

Test Item	Standard Value
Test Material	PTFE(ROHS)
Insulation resistance(20℃ MΩ*m	1000
Vol. Tesr(AC.V.60S) (V)	2000
Flammability Test	Horizontal flame
Max.DC Resistance(20℃ Ω/km)	127(MAX)

Customer Approve

Seal & Stamp

Signature:

Date:

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.