NO	DESCRIPTION	DATE
1	BACKGROUND FORMAT UPDATED	06.26.06'
2	BACKGROUND FORMAT UPDATED	11.25.08'





STRIPPING DIMENSION

1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-1 GHz

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

4.1 FOR USE WITH RG59U OR SIMILAR STYLE CABLE

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
2	BODY	BRASS	1	NICKEL 100μ" MIN.
1	NUT	BRASS	1	NICKEL 100μ" MIN.

APPROVED by _____ DATE: _____

DESCRIPTION	F STRAIGHT PLUG CRIMP								
製圖	DRAWN: Kristina	TOLERANCE		品名 TITLE	18-07-2 NICKEL 59U \ROHS COMPLIANT	日期	DATE 03.05.93'	版次	REV. A-2
檢圖	CHECK: Arc	.X	±0.2	單位	UNIT mm(in)	DWG.NO.	18-0050		
		.XX	±0.1						
認定	APPROVAL: Angela	.XXX	±0.05	比例	SCALE 4:1				
		ANGLE	±5°						