ENGLISH

Datasheet

Stock No: 429-656

RS Pro Straight Cable Conduit Fitting, Nylon 66 16mm nominal size IP55

Product Details

Fittings

IP55 (with Fittings)
Conduit -50°C → +100°C, fittings -25°C → +50°C operating temperature
Crush resistant to BS6099
1.5mm pitch straight fittings supplied with lockring
Self extinguishing nylon to UL94VO
Resistant to: nitric acid, sulphuric acid, detergent, diesel and white spirit

Specifications:

Fitting Type	Straight
Nominal Size	16mm
Material	Nylon 66
Colour	Grey
IP Rating	IP55
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+50°C