



BF0910A



BF2600A



BF3000



B11500



B12500



BF09T4A



B115400



BF004A

type	rated current (AC1)	current (AC3)	kW rating (AC3) 400V	control	description	auxiliary contacts
Three-pole contactors (Ui 690V) / AC control circuit						
BF0910A	25A	9A	4.2kW	AC	3-pole contactor	1NO
BF0901A	25A	9A	4.2kW	AC	3-pole contactor	1NC
BF1210A	28A	12A	5.7kW	AC	3-pole contactor	1NO
BF1201A	28A	12A	5.7kW	AC	3-pole contactor	1NC
BF1810A	32A	18A	7.5kW	AC	3-pole contactor	1NO
BF1801A	32A	18A	7.5kW	AC	3-pole contactor	1NC
BF2510A	32A	25A	12.5kW	AC	3-pole contactor	1NO
BF2501A	32A	25A	12.5kW	AC	3-pole contactor	1NC
BF2600A	45A	26A	13.0kW	AC	3-pole contactor	—
BF3200A	56A	32A	16.0kW	AC	3-pole contactor	—
BF3800A	56A	38A	18.5kW	AC	3-pole contactor	—
Three-pole contactors (Ui 1000V) / AC control circuit						
BF5000	90A	50A	25kW	AC	3-pole contactor	—
BF6500	110A	65A	33kW	AC	3-pole contactor	—
BF8000	125A	80A	41kW	AC	3-pole contactor	—
BF9500	125A	95A	50kW	AC	3-pole contactor	—
BF11000	125A	110A	61kW	AC	3-pole contactor	—
B11500	160A	110A	61kW	AC	3-pole contactor	—
B14500	250A	150A	80kW	AC	3-pole contactor	—
B18000	275A	185A	100kW	AC	3-pole contactor	—
B25000	350A	265A	140kW	AC	3-pole contactor	—
B31000	450A	320A	170kW	AC	3-pole contactor	—
B40000	550A	420A	225kW	AC	3-pole contactor	—
B50000	700A	520A	290kW	AC	3-pole contactor	—
B63000	800A	630A	335kW	AC	3-pole contactor	—
			(AC1)			
B125024	1250A	—	830kW	AC	3-pole contactor	—
B160024	1600A	—	950kW	AC	3-pole contactor	—
Four-pole contactors (Ui 690V) / AC control circuit						
type	rated current (AC1)		kW (AC1) 230V 400V	control	description	main contacts
BF09T4A	25A	9.5	16	AC	4-pole contactor	4NO
BF12T4A	28A	10	18	AC	4-pole contactor	4NO
BF18T4A	32A	12	21	AC	4-pole contactor	4NO
BF26T4A	45A	17	30	AC	4-pole contactor	4NO
BF38T4A	56A	21	36	AC	4-pole contactor	4NO
BF09T2A	25A	9.5	16	AC	4-pole contactor	2NO+2NC
BF18T2A	32A	10	18	AC	4-pole contactor	2NO+2NC
BF26T2A	45A	12	21	AC	4-pole contactor	2NO+2NC
BF38T2A	56A	17	30	AC	4-pole contactor	2NO+2NC
BF18T0A	32A	21	36	AC	4-pole contactor	4NC
Four-pole contactors (Ui 1000V) / AC control circuit						
BF5040	90A	34	59	AC	4-pole contactor	4NO
BF6540	110A	41	72	AC	4-pole contactor	4NO
BF8040	125A	47	82	AC	4-pole contactor	4NO
B115400	160A	57	98	AC	4-pole contactor	4NO
B145400	250A	91	150	AC	4-pole contactor	4NO
B180400	275A	95	160	AC	4-pole contactor	4NO
B250400	350A	124	214	AC	4-pole contactor	4NO
B310400	450A	158	270	AC	4-pole contactor	4NO
B400400	550A	200	345	AC	4-pole contactor	4NO
B500400	700A	252	438	AC	4-pole contactor	4NO
B630400	800A	288	500	AC	4-pole contactor	4NO
Control relays / AC control circuit						auxiliary
BF0040A	10A	—	—	AC	control relay	4NO
BF0031A	10A	—	—	AC	control relay	3NO+1NC
BF0022A	10A	—	—	AC	control relay	2NO+2NC
BF0004A	10A	—	—	AC	control relay	4NC