



ENGLISH

Datasheet


Stock No: 822-9644

RS Pro Round Top Cable Gland



Features:

- Material: UL approved Nylon 66, 94V-2
- Colour: Grey, available in other colours.
- Application: Suit a variety of applications, and diverse industries
- Function: Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal, and then tighten up the nut to hold cables in position
- Simply and quickly fixed, high degree of the protection IP68 preventing dust and water
- PG THREAD (DIN STANDARD) WITH WASHER
- Protection: IP68 (only if the washer is assembled)



| RS PART NUMBER | DESCRIPTION | D1 | D2 | B1 | L1 | L2 | L3 | Cable Range | COLOR | Packsize |
|----------------|-----------------------------------------|------|------|------|------|------|------|-------------|-------|----------|
| 8229640 | round top cable gland PG7 Grey IP68 | 12.5 | 8.3 | 6.9 | 7.9 | 20 | 13.3 | 3.5~6 | GREY | 10 |
| 8229644 | round top cable gland PG9 Grey IP68 | 15.2 | 10.5 | 8 | 7.9 | 22 | 15.1 | 4~8 | | |
| 8229653 | round top cable gland PG11 Grey IP68 | 18.3 | 13.2 | 10.5 | 7.9 | 23.7 | 18.3 | 5~10 | | |
| 8229656 | round top cable gland PG13.5 Grey IP68 | 20.4 | 15.5 | 12 | 8.9 | 24.6 | 18.9 | 6~12 | | |
| 8229650 | round top cable gland PG16 Grey IP68 | 22.5 | 17.2 | 14 | 9.8 | 26.2 | 19.5 | 10~14 | | |
| 8229669 | round top cable gland PG21 Grey IP68 | 28.3 | 22.4 | 18.4 | 10.8 | 30 | 23.7 | 13~18 | | |
| 8229662 | round top cable gland PG29 Grey IP68 | 37 | 30.6 | 25 | 10.8 | 35 | 27.4 | 18~25 | BLACK | |
| 8229666 | round top cable gland PG7 Black IP68 | 12.5 | 8.3 | 6.9 | 7.9 | 20 | 13.3 | 3.5~6 | | |
| 8229675 | round top cable gland PG9 Black IP68 | 15.2 | 10.5 | 8 | 7.9 | 22 | 15.1 | 4~8 | | |
| 8229678 | round top cable gland PG11 Black IP68 | 18.3 | 13.2 | 10.5 | 7.9 | 23.7 | 18.3 | 5~10 | | |
| 8229672 | round top cable gland PG13.5 Black IP68 | 20.4 | 15.5 | 12 | 8.9 | 24.6 | 18.9 | 6~12 | | |
| 8229681 | round top cable gland PG16 Black IP68 | 22.5 | 17.2 | 14 | 9.8 | 26.2 | 19.5 | 10~14 | | |
| 8229684 | round top cable gland PG21 Black IP68 | 28.3 | 22.4 | 18.4 | 10.8 | 30 | 23.7 | 13~18 | | |
| 8229688 | round top cable gland PG29 Black IP68 | 37 | 30.6 | 25 | 10.8 | 35 | 27.4 | 18~25 | | |