

Fuse module - EMG 45-SI8S - 2954950

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Fuse module, for 8 cartridge fuse inserts, 5 x 20 mm, common connection point

The illustration shows version EMG 45-SI/K, with 8 cartridge fuse holders



Key commercial data

Packing unit	5 pc
GTIN	 4 017918 085216
Weight per Piece (excluding packing)	142.34 g
Custom tariff number	85363010
Country of origin	Germany

Technical data

Dimensions

Width	45 mm
Depth	62 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 50 °C

General

Nominal voltage U_N	250 V AC
Cartridge fuse inserts	Max. 6.3 A/250 V AC (between two terminal blocks) Max. 3 A/250 V AC (for simultaneous loading of inserts)
Mounting position	any
Assembly instructions	In rows with zero spacing
Standards/regulations	IEC 664

Fuse module - EMG 45-SI8S - 2954950

Technical data

General

	IEC 664 A
	DIN VDE 0110-1
	DIN VDE 0160
	DIN VDE 0109-11, draft
Pollution degree	2
Surge voltage category	III

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

Classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

ETIM

ETIM 2.0	EC000036
ETIM 3.0	EC000036
ETIM 4.0	EC000036
ETIM 5.0	EC000036

UNSPSC

UNSPSC 6.01	30212005
UNSPSC 7.0901	39121605
UNSPSC 11	39121605
UNSPSC 12.01	39121605
UNSPSC 13.2	39121605

Fuse module - EMG 45-SI8S - 2954950

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Accessories

Accessories

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

Drawings

Fuse module - EMG 45-SI8S - 2954950

Circuit diagram

