

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Printing set, consisting of: 1 x THERMOMARK ROLL, Order No. 5146477, 1 x THERMOMARK CARD, Order No. 5146464, 1 x MARKING NOTEBOOK (without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL, country-specific keyboard version and operating system

Why buy this product

- Includes the THERMOMARK CARD printer for all materials in UniCard (UCT) and UniSheet (US) format
- Includes the THERMOMARK ROLL printer for all labels and shrink sleeves in roll format
- MARKING BOX is the complete labeling system for all terminal, conductor, cable, and device marking applications



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 694933
Weight per Piece (excluding packing)	14920.8 g
Custom tariff number	84714900
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Interface	10/100 Mbps Ethernet
	USB 2.0

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Classifications

eCl@ss

eCl@ss 4.0	27060701
------------	----------

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Classifications

eCl@ss

eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001675
ETIM 5.0	EC001672

UNSPSC

UNSPSC 6.01	27121706
UNSPSC 7.0901	27121706
UNSPSC 11	27121706
UNSPSC 12.01	27121706
UNSPSC 13.2	27121706

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: blue

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: red

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon for EMLHT high-temperature labels, length: 300 m, width: 110 mm, ink color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: white

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color white

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Magazine

Magazine - THERMOMARK CARD-UCT-MAG1 - 5146480



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TM..., UCT1-TM..., UCT5-TM...)

Magazine - THERMOMARK CARD-UCT-MAG2 - 5146563



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TMF...)

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Magazine - THERMOMARK CARD-UCT-MAG3 - 5146613



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMS...)

Magazine - THERMOMARK CARD-UCT-MAG4 - 5146614



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT1-TMF...)

Magazine - THERMOMARK CARD-UCT-MAG5 - 5146615



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT2-TM...)

Magazine - THERMOMARK CARD-UCT-MAG6 - 5146616



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT2F-TM...)

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Magazine - THERMOMARK CARD-UCT-MAG7 - 0801734



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMT...)

Magazine - THERMOMARK CARD-UCT-MAG8 - 0801735



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (10 x 7), UCT-EM (15 x 10), UCT-EM (17.5 x 8)

Magazine - THERMOMARK CARD-UCT-MAG10 - 0801737



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (30 x 5)

Magazine - THERMOMARK CARD-UCT-MAG11 - 0801738



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (17 x 10)

Magazine - THERMOMARK CARD-UCT-MAG12 - 0830399



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (10 x 8) and UCT-EM (12 x 7)

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Magazine - THERMOMARK CARD-UCT-MAG9 - 0801736



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (12 x 3.3) and UCT-EM (12 x 6)

Magazine - THERMOMARK CARD-UCT-MAG13 - 0830400



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (10 x 5)

Magazine - THERMOMARK CARD-UCT-MAG14 - 0830401



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (21 x 8)

Magazine - THERMOMARK CARD-UCT-MAG15 - 0830402



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (20 x 9)

Magazine - THERMOMARK CARD-UCT-MAG16 - 0830403



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (17 x 9) and UCT-EM (17.5 x 9)

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Magazine - THERMOMARK CARD-UCT-MAG17 - 0830404



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (18 x 8)

Magazine - THERMOMARK CARD-UCT-MAG18 - 0830405



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (17.5 x 7.5)

Magazine - THERMOMARK CARD-UCT-MAG19 - 0830406



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (15 x 10)

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for easy planning of Phoenix Contact on DIN rails together with the integrated TRABTECH-select software module for planning comprehensive surge protection concepts.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multi-lingual software for terminal strip project planning. A marking module allows professional labeling of markers and labels for marking terminal blocks, conductors, cables and devices. The additionally integrated software module TRABTECH-select for planning comprehensive surge protection concepts.

Printing system accessories

Thermal transfer printer set - MARKING BOX PT PT - 0801748

Accessories

Cutter - THERMOMARK ROLL-CUTTER - 5146422



Cutter, for the THERMOMARK ROLL, cutter width: 110 mm, suitable for: labels, continuous media up to 110 mm wide, PMM continuous media up to 50.1 mm in diameter, TMT continuous media, and EMT (EX15)R

Cutter - THERMOMARK ROLL-CUTTER/P - 5146435



Perforation cutter, for the THERMOMARK ROLL, cutter width: 60 mm, suitable for: WMS continuous media up to 25.8 mm in diameter, TMT continuous media, and EMT (EX15)R

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Transport case - TL CASE - 0800613



Transport case for THERMOMARK printer, rounded profile case with aluminum frame
