

50PC. AUTO REPAIR MASTER TOOL SET

New

PART NO.	CONTENT		G.W.(kg)
09508	50PC.	2	19.2

DESCRIPTION:
 11 - 1/2"Dr. 12pt. Metric Sockets 8, 10, 12, 17, 18, 19, 20, 21, 22, 24, 27mm
 1 - 1/2"Dr. 50L Bit Socket Hex 17mm
 1 - 1/2"Dr. 100L Bit Socket Hex 7mm
 9 - 1/2"Dr. Extra Long Bit Sockets
 Hex 6x70, 8x120, 6x250, 5x180, 6x140, 10x140mm
 Splines M8x100mm, M10x120mm, M10x140mm
 9 - Extra Long Arm Ball Point Hex Key 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm
 2 - 1/2"Dr. Spark Plug Sockets 16, 21mm
 2 - Go Through Screwdrivers Slotted 6x100mm Phillips #6x100mm
 15 - Accessories
 1/2"Dr. Quick-Release Ratchet
 1/2"Dr. Sliding T-Bar
 1/2"Dr. Wobble Extension Bars 5", 10"
 1/2"Dr. Universal Joint
 1/2"Dr. Offset Handle 260mm
 3/8"Dr. Two Way Oil Filter Wrench with Adapter
 Raise Panel Combination Wrenches 8, 10, 13, 17, 19, 22mm
 Front shock Absorption Install Tool
 Shock Absorption Install Socket



56PC. AUTO REPAIR MASTER TOOL SET

New

PART NO.	CONTENT		G.W.(kg)
09509	56PC.	4	20.2

DESCRIPTION:
 15 - 3/8"Dr. 6pt. Metric Sockets 7, 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24mm
 15 - 1/4"Dr. 25L Bits
 Slotted 4, 5, 6.5mm
 Phillips #1, #3
 Hex 3, 4, 5, 6mm
 Tamper Torx® T10, T15, T20, T25, T30, T40
 2 - 3/8"Dr. Spark Plug Sockets 16, 21mm
 2 - Go Through Screwdrivers Slotted 6x100mm Phillips #2x100mm
 22 - Accessories
 1/4"Dr. Spinner Handle
 1/4"Dr. Adapter
 1/4"Dr. x 1/4" Shank Bit Coupler
 3/8"Dr. Quick-Release Ratchet
 3/8"Dr. Wobble Extension Bars 3", 10"
 3/8"Dr. Universal Joint
 3/8"Dr. Adapter
 1/2"Dr. 3-Way Adapter
 Combination Wrenches 8, 10, 12, 13, 14, 15, 16, 17, 18, 19, 22mm
 Long Nose Pliers 6"
 Slip Joint Pliers 8"



5PC. EXTRACTOR SET

PART NO.	CONTENT			G.W.(kg)
09704	5PC.	20	120	15.4

DESCRIPTION:
 2.5mm, 3.0mm, 4.5mm,
 6.0mm, 8.0mm

- Tapered extractors for broken screws and studs.
- Made from hardened and tempered steel (Cr-Mo).
 (For removing screws and studs that cannot be held firmly)



⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

5PC. TAPERED SET

New

PART NO.	CONTENT			G.W.(kg)
09704A	5PC.	6	72	11.5

DESCRIPTION:
 3.3mm, 5.3mm, 6.4mm,
 8.8mm, 11.2mm

- Tapered extractors for broken screws and studs.
- Made from hardened and tempered steel (Cr-Mo).
 (For removing screws and studs that cannot be held firmly)



⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

5PC. HOOK AND PICK SET

New


PART NO.	CONTENT			G.W.(kg)
09709	5PC.	20	200	11.0



CROSS WRENCH

New

PART NO.	Size MM		G.W.(kg)
48101	17, 19, 21, 1/2"DR.	12	17.5



⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

DETECTING SCREWDRIVER

New

PART NO.			G.W.(kg)
62601	24	240	8.4



⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

2 JAW GEAR PULLERS

PART NO.	SIZE INCHES	D MM	L MM	H MM		G.W.(kg)
90623	3"	75	125	60	48	21.6
90624	4"	100	155	70-95	24	20.9
90626	6"	150	240	120-160	16	22.3
90628	8"	200	325	175-235	6	25.1

