



MASTER LEDtube Performance

MASTER LEDtube PERF 1500mm 31W830 T8 I ROT

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Product data

• General Characteristics

Main Application	Industrial
Cap-Base	G13
Rated Lifetime	50000 hr
Nominal Lifetime hours	50000 hr

• Light Technical Characteristics

Colour Code	830
Beam Angle	140 D
Correlated Colour Temperature	3000 K
Colour rendering index	85
Rated Luminous Flux	2800 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	<5
Rated Beam Angle	140 D

• Electrical Characteristics

Wattage	31 W
Voltage	220-240 V
Line Frequency	50/60 Hz
Power Factor	0.9 (min) -
Dimmable	No
Rated Wattage	31 W
Starting Time	0.5 (max) s
Warm-up Time to 60% Light Outp	instant full light
Energy saving product	Yes
Suitable for accent lighting	No

• Temperature Characteristics

T-case maximum	55 (max) C
Operating temperature	-30 (min), 45 (max) C
T-Storage	-40 (min), 65 (max) C

• Environmental characteristics

Energy Efficiency Label (EEL)	A+
-------------------------------	----

• Measuring Conditions

Switching cycle	50000X
-----------------	--------

• Product Dimensions

Length A1	1500.0 mm
Fixing Hole Distance A2 Length	1507.0 mm
Length A3	1514.0 mm
Mounting hole diameter	25.68 mm
Circular outline dimension	28 mm

• Approval & Application Chars

VDE marking	No
CE marking	Yes
UL certificate	No
RoHS compliance	Yes
KEMA Keur certificate	Yes



PHILIPS


MASTER LEDtube Performance

• Product Data

Order code 690085 00
 Full product code 871829169008500
 Full product name MASTER LEDtube PERF 1500mm
 31W830 T8 I ROT
 Order product name MAS LEDtube PERF 1500mm
 31W830 T8 I ROT
 Pieces per pack 1
 Packing configuration 10


Packs per outerbox 10
 Bar code on pack - EAN1 8718291690085
 Bar code on outerbox - EAN3 8718291690092
 Logistic code(s) - 12NC 929000282902
 Net weight per piece 0.450 kg

Dimensional drawing




MASTER LEDtube PERF 1500mm 31W830 T8 I ROT

Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	D1 (Norm)	D2 (Norm)
TLED PERF 1500mm 31W830 T8 I ROT	1500.0	1507.0	1514.0	25.68	28



G13

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, June 28
 data subject to change