


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [55560-0347](#)
Status: **Active**
Overview: SlimStack™ 0.50mm Pitch Board-to-Board Connectors
Description: 0.50mm Pitch SlimStack™ Plug, Surface Mount, Dual Row, Vertical, 1.50mm Stack Height, 34 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-55560-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-54722-009 \(PDF\)](#)



General

Product Family	PCB Headers
Series	55560
Application	Board-to-Board, Signal
Overview	SlimStack™ 0.50mm Pitch Board-to-Board Connectors
Product Name	SlimStack™
UPC	756054621899

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	46.106/mg
Number of Rows	2
Orientation	Vertical
PC Tail Length	0.74mm
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.254µm
Plating min - Termination	0.102µm
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-55560-001
-------------------------	---------------

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[55560Series](#)

Mates With

[54722 PCB Receptacle](#)

Product Specification

Sales Drawing

PS-54722-009, RPS-54722-018, RPS-54722-026,
RPS-54722-028, RPS-54722-029, RPS-54722-030,
RPS-54722-034
SD-55560-006, SD-55560-007

This document was generated on 08/12/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION