

Cable glands



Pressure compensation element DAE M12, up to IP 69K

Model	Order no.	Colour	Note
DAE M12	52041000	Light grey	M 12 x 1.5
DAE M12	52042000	Black	M 12 x 1.5

Scope of delivery: 5 pieces

Note: Air, which may create a vacuum in the enclosure when it cools, can suck in water etc. through the seal into the enclosure, which means that ingress protection can no longer be guaranteed. BOPLA's product range includes the pressure compensation element to compensate such variations in pressure caused by differences in temperature. When fitted, the DAE provides IP 69 K protection.



Metric cable glands MBF, polyamide, light grey, IP 68

Model	Order no.	Note
MBF 12	12002100	M 12 x 1.5; cable diameter 3-6 mm
MBF 16	12002200	M 16 x 1.5; cable diameter 5-10 mm
MBF 20	12002300	M 20 x 1.5; cable diameter 8-13 mm
MBF 25	12002400	M 25 x 1.5; cable diameter 11-17 mm
MBF 32	12002500	M 32 x 1.5; cable diameter 15-21 mm
MBF 40	12002600	M 40 x 1.5; cable diameter 19-28 mm



Metric cable glands with anti-kink protection MBFK, polyamide, light grey, IP 68

Model	Order no.	Note
MBFK 12	12002103	M 12 x 1.5; cable diameter 3-6.5 mm
MBFK 16	12002210*	M 16 x 1.5; cable diameter 5-10 mm
MBFK 20-1	12002303	M 20 x 1.5; cable diameter 6-12 mm
MBFK 20-2	12002306*	M 20 x 1.5; cable diameter 10-14 mm
MBFK 25	12002401*	M 25 x 1.5; cable diameter 13-18 mm

Note: * = Available on request



Metric cable glands MPOZ, polyamide, light grey, IP 65

Model	Order no.	Note
MPOZ 12-1	12151800	M 12 x 1.5; cable diameter 4-6 mm
MPOZ 12-2	12151900	M 12 x 1.5; cable diameter 6-8 mm
MPOZ 16	12152000	M 16 x 1.5; cable diameter 6-8 mm
MPOZ 20-1	12152100	M 20 x 1.5; cable diameter 8-10 mm
MPOZ 20-2	12152200	M 20 x 1.5; cable diameter 10-12 mm
MPOZ 20-3	12152300	M 20 x 1.5; cable diameter 12-14 mm
MPOZ 25-2	12152400	M 25 x 1.5; cable diameter 14-18 mm
MPOZ 32	12152500	M 32 x 1.5; cable diameter 18-24 mm