

Crimping pliers - CRIMPFOX-M - 1212072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Basic pliers, for accommodating dies for a wide range of contact types

Why buy this product

- The variety of inserts makes it a space-saving universal tool for all applications
- One of the key features of the CRIMPFOX-M crimping pliers is the way the crimp inserts can be quickly replaced without the need for tools



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 452519
Weight per Piece (excluding packing)	499.0 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	234 mm
Height	31 mm
Width (a)	64 mm

General

Color	black
Compression	universal

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301

Crimping pliers - CRIMPFOX-M - 1212072

Classifications

eCl@ss

eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Die

Crimping pliers - CRIMPFOX-M - 1212072

Accessories

Replacement die - CRIMPFOX-M SR 6-1/DIE - 1212471



Die, for MC3 solar connectors, lateral entry, 2.5 - 6 mm²

Replacement die - CRIMPFOX-M SR 6-2/DIE - 1212472



Die, for MC4 solar connectors, lateral entry, 2.5 - 6 mm²

Replacement die - CRIMPFOX-M SR 6-3/DIE - 1212473



Die, for SOLARLOK solar connectors, lateral entry, 2.5 - 6 mm²

Replacement die - CRIMPFOX-M 10/DIE - 1212080



Die, for Crimpfox-M, for ferrules 0.25 - 10 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M 25/DIE - 1212081



Die, for Crimpfox-M, for ferrules 16 - 25 mm², packed in a serial storage box

Crimping pliers - CRIMPFOX-M - 1212072

Accessories

Replacement die - CRIMPFOX-M 50/DIE - 1212082



Die, for Crimpfox-M, for ferrules 35 - 50 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M RCI 2,5/DIE - 1212074



Die, for Crimpfox-M, for insulated cable lugs 0.5 - 1.5 mm² and 1.5 - 2.5 mm² (red, blue), packed in a serial storage box

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm² and 4 - 6 mm² (light green, yellow), packed in a serial storage box

Replacement die - CRIMPFOX-M RC 2,5/DIE - 1212078



Die, for Crimpfox-M, for non-insulated cable lugs 0.75 - 2.5 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M RC 6/DIE - 1212079



Die, for Crimpfox-M, for non-insulated cable lugs 0.5 - 6 mm², packed in a serial storage box

Crimping pliers - CRIMPFOX-M - 1212072

Accessories

Replacement die - CRIMPFOX-M RC 10/DIE - 1212077



Die, for Crimpfox-M, for non-insulated cable lugs 4 - 10 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M SC 1/DIE - 1212083



Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.1 - 1 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M SC 2,5/DIE - 1212084



Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.5 - 2.5 mm²

Replacement die - CRIMPFOX-M SC 6/DIE - 1212085



Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.5 - 6 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M TC 4/DIE - 1212075



Die, for Crimpfox-M, for turned contacts 0.14 - 4 mm², packed in a serial storage box

Crimping pliers - CRIMPFOX-M - 1212072

Accessories

Replacement die - CRIMPFOX-M TC 10/DIE - 1212076



Die, for Crimpfox-M, for turned contacts 6 - 10 mm², packed in a serial storage box

Replacement die - CRIMPFOX-M CX-1/DIE - 1212087



Die, for Crimpfox-M, for coaxial connectors: RG 174, RG 179 / BNC / TNC , packed in a serial storage box

Replacement die - CRIMPFOX-M CX-2/DIE - 1212088



Die, for Crimpfox-M, for coaxial connectors (BNC/TNC) RG 58/ 59/ 62/ 71, packed in a serial storage box

Replacement die - CRIMPFOX-M CX-3/DIE - 1212089



Die, for Crimpfox-M, for coaxial connectors: CATV RG 6,59, packed in a serial storage box

Replacement die - CRIMPFOX-M RJ45/DIE - 1212090



Die, for Crimpfox-M, for unshielded RJ45 connectors, packed in a serial storage box

Crimping pliers - CRIMPFOX-M - 1212072

Accessories

Replacement die - CRIMPFOX-M RJ11/DIE - 1212091



Die, for Crimpfox-M, for unshielded RJ11 connectors, packed in a serial storage box

Replacement die - CRIMPFOX-M HS-1/DIE - 1212282



Die, for CRIMPFOX-M, for 0.1 - 0.4 mm² and 4 - 6 mm² shrink connectors (light green, yellow), packed in a modular storage box
