

Conductor marker - UC-WMC 3,1 (23X4) - 0818218

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Conductor marker, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Clip on, Cable diameter: 1.9-3.1 mm, Lettering field: 23 x 4 mm



Why buy this product

- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- One-handed assembly
- Can be clipped on even after wiring has been completed
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Two labeling areas that are clearly legible at all times
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers support multi-line labeling
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 133524
Weight per Piece (excluding packing)	9.95 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Width (a)	23 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2

Conductor marker - UC-WMC 3,1 (23X4) - 0818218

Technical data

General

Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	12
Number of individual labels per row	4

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 1 - 5146079



Magazine, for CMS-P1-PLOTTER, for accommodating UC-TM..., UC-TMN..., UC-WMC 3,1..., UC-WMTBA...

