



ENGLISH

Datasheet

Aluminium Enclosure, IP65, 102 x 210 x 242mm

RS Stock number 229-0340




| | |
|---------------------|--------------------|
| Body Material | Die Cast Aluminium |
| Colour | Natural |
| External Dimensions | 102 x 210 x 242mm |
| External Height | 242 mm |
| External Length | 102 mm |
| External Width | 210 mm |
| IP Rating | IP65 |



ENGLISH

Dimensions (mm)


| | A* | B* | H | C* | D* | E* | F* |
|----------|-----|-----|-----|------|------|-----|-----|
| 282-1102 | 102 | 102 | 71 | 89.5 | 89.5 | 63 | 63 |
| 229-0334 | 135 | 110 | 71 | 127 | 102 | 91 | 66 |
| 229-0362 | 160 | 135 | 81 | 153 | 128 | 116 | 91 |
| 229-0356 | 185 | 160 | 96 | 177 | 152 | 140 | 115 |
| 229-0340 | 245 | 210 | 102 | 238 | 203 | 201 | 166 |



5.00
7.25
8.25
11.95
18.25

* Maximum useful size

| | I | L | M | N | P | Q | S | T dia | KC | KT |
|----------|----|-----|-----|-----|------|-----|----|-------|--------|--------|
| 282-1102 | 65 | 106 | 106 | 66 | 56.5 | 45 | 10 | 4 | 4 x M5 | 1 x M5 |
| 229-0334 | 64 | 142 | 117 | 98 | 47 | 51 | 13 | 4 | 4 x M5 | 1 x M5 |
| 229-0362 | 74 | 167 | 142 | 124 | 58 | 69 | 13 | 4 | 4 x M5 | 2 x M5 |
| 229-0356 | 89 | 192 | 167 | 146 | 72 | 76 | 13 | 4 | 4 x M5 | 2 x M5 |
| 229-0340 | 94 | 254 | 219 | 208 | 77 | 101 | 13 | 4 | 4 x M5 | 2 x M5 |



Dimensions (mm)

| | V | Z | Type | X1 | Y1 | X2 | Y2 |
|----------|-------|-------|-------|-----|-----|-----|-----|
| 282-1102 | 32 | 72 | A | 82 | 111 | 82 | 111 |
| 229-0334 | 65 | 80 | A | 114 | 119 | 89 | 144 |
| 229-0362 | 88 | 104 | A + B | 140 | 145 | 115 | 170 |
| 229-0356 | 114.5 | 129.5 | A + B | 164 | 169 | 139 | 195 |
| 229-0340 | 172 | 178 | A + B | 224 | 219 | 189 | 254 |

