

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 E14 12W SLV

0035208

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035208
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	Spiral
Lamp finish	Frosted
Dimmable	No
Cap/Base	E14
Type	SPIRAL
EAN code	5410288352084
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	600
Efficacy (Rated) (lm/w)	50
Watt (Nominal) (W)	12
Equivalent watt (W)	50
Voltage (V)	220-240

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 E14 12W SLV

0035208

DATA TABLE

General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035208
Energy saving lamp	Yes
Average life (Rated) (h)	10000
Energy class	A
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	Spiral
Dimmable	No
Cap/Base	E14
Type	SPIRAL
EAN code	5410288352084
E-number FI	4940299
E-number SE	8357557
Long description	
Product name	ML SPIRAL 827 E14 12W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.0
Warm-up time to 60% of full light (max) (s)	<40
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	600
Lumen maintenance at end of nominal life (%)	65
Luminous flux (Nominal) (lm)	600

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 E14 12W SLV

0035208

Electrical data

kWh per 1000 hours burning time	12
Efficacy (Rated) (lm/w)	50
Watt (Rated) (W)	12
Watt (Nominal) (W)	12
Equivalent watt (W)	50
Voltage (V)	220-240
Lamp power factor	=0.55

Physical data


Weight (kg)	0.04
Lamp Length (mm) - C/L	97.5±3
Max. Lamp Diameter (mm) - D	45±1
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	11.50 x 4.80 x 4.80
Outer package dimensions (L x W x H) (cm)	26.00 x 13.50 x 11.50

Mini-Lynx Fast Start Spiro

ML SPIRAL 827 E14 12W SLV

0035208

TECHNICAL DRAWINGS



ENERGY LABEL

