

## Fuse plug - ST-SI-UK 4 - 0921011

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, Nominal current: 6.3 A, Length: 33.1 mm, Width: 6.1 mm, Height: 26.5 mm, Color: black



### Key commercial data

Packing unit	50 pc
GTIN	 4 017918 010270
Weight per Piece (excluding packing)	5.73 g
Custom tariff number	85363010
Country of origin	Poland

### Technical data

#### General

Note	If the fuse is defective, the downstream circuit is not off load
Color	black
Insulating material	PA
Inflammability class according to UL 94	V2

#### Dimensions

Width	6.1 mm
Length	33.1 mm
Height NS 35/7,5	26.5 mm

#### General

Fuse	G / 5 x 20
Insulating material group	CTI 600
Current	6.3 A
Nominal current $I_N$	6.3 A
Nominal voltage $U_N$	250 V

# Fuse plug - ST-SI-UK 4 - 0921011

## Classifications

### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 5.0	EC002018

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals


#### Approvals

CSA / UL Recognized / cUL Recognized / ABS / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

### Approval details

	
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	300 V

# Fuse plug - ST-SI-UK 4 - 0921011

## Approvals

UL Recognized	
Nominal current IN	6.3 A
Nominal voltage UN	300 V

cUL Recognized	
Nominal current IN	6.3 A
Nominal voltage UN	300 V

ABS	
Nominal current IN	10 A
Nominal voltage UN	300 V

EAC	
-----	--

cULus Recognized	
------------------	--

## Accessories

Accessories

Documentation

Mounting material - ST-IL - 3039900

Operating decal for the ST terminal block

