

General Information

Extended Product Type:	PC6-2
Product ID:	1SNA113546R1400
EAN:	3472591135466
Catalog Description:	PC6-2 Lateral Jumper Bars Grey
Long Description:	PC6-2 - Lateral Jumper Bars - 2 poles - Grey - 6mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Lateral Jumper Bars

Ordering

EAN:	3472591135466
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	2 g
----------------------------	-----

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.02 kg
Package Level 1 EAN:	3472591135466
Package Level 2 Units:	2000 piece
Package Level 3 Units:	360000 piece

Additional Information

Color:	Grey
Function:	Lateral Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Placed in the compression clamp before tightening the screw, above the eventual conductor.
Product Main Type:	PC
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 35 A
Sub-Function 2:	Lateral
Suitable For:	C2.5/6 C4/6 C4/6.S C4/6.SF C4/6.SFD24 D4/6.ADO D4/6.ADO.NC D4/6.D2.ADO D6/8.D2.ADO DB4/6.ADO DH4/6.ADO DR4/6.ADO DRE4/6.ADO DS4/6.ADO DSE4/6.ADO M4/6 M4/6.3A M4/6.3A.NC M4/6.4A M4/6.D2.2S2 M4/6.D2.S1R M4/6.NC MS4/6 ZS4-PE-R2 ZS4-R2 ZS4-SF ZS4-SF-R ZS4-SF-T ZS4-SP-R1 ZS4-SP-T2-R1 ZS4-S-R1 ZS4-S-T-R1 ZS6-S

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: 1SNC160001C0207-CH-J Accessories

Declaration of Conformity - CE: 1SND225001C1009

Classifications

ETIM 4.0: EC000489 - Cross-connector for terminal block

ETIM 5.0: EC000489 - Cross-connector for terminal block

Object Classification Code: X

