


Uniboot

As Supplied (a)



After Unrestricted Recovery (b)



Applications

Use to provide abrasion protection for connectors. The flexibility of design allows a variety of cable outlet angles. When installed on a spin-coupling adapter, cold reentry to the

connector is possible by compressing the molded part. When used with adhesive it provides environmental sealing.

Materials Available

Material*	Material Description	Precoating No.	Adhesive Part No.**
-50	Viton® polymer blend	N/A	S-1125
-51	Elastomer polymer blend	/164	S-1124
-71	Flexible polyolefin	/42 or /86	S-1017 or S-1048

*For more information, please see the appropriate material page in this section.

**For more information, please see section 5.

Product Dimensions

Part No.	H			J			K Max. b	P ±10% b	JO ±10% b	S ±.03[0.76] b	T ±.03[0.76] b	W Min. b	B Nom. b
	Min.		Max. b	Min.		Max. b							
	a -50, -51	a -71		a -50, -51	a -71								
202C611	14.2 [56]	17.5 [69]	6.9 [27]	11.2 [44]	14.2 [56]	4.8 [19]	21.1 [83]	120.7 [4.75]	17.5 [69]	1.52 [06]	1.27 [05]	0.33 [013]	62.5 [2.46]
202C621	22.4 [88]	26.4 [1.04]	11.7 [46]	17.8 [70]	26.4 [1.04]	8.1 [32]	26.7 [1.05]	133.4 [5.25]	19.0 [78]	1.52 [06]	1.27 [05]	0.46 [018]	67.8 [2.67]
202C632	34.0 [1.34]	38.1 [1.50]	17.5 [69]	26.9 [1.06]	38.1 [1.50]	12.7 [50]	32.8 [1.29]	146.1 [5.75]	22.4 [88]	1.78 [07]	1.27 [05]	0.51 [020]	73.4 [2.89]
202C642	44.2 [1.74]	47.8 [1.88]	22.4 [88]	36.6 [1.44]	47.8 [1.88]	17.5 [69]	37.8 [1.49]	158.8 [6.25]	25.4 [1.00]	1.78 [07]	1.27 [05]	0.61 [024]	78.2 [3.08]
202C653	21.2 [53.8]	54.9 [2.16]	27.9 [1.10]	45.7 [1.80]	54.9 [2.16]	22.4 [88]	42.9 [1.69]	171.5 [6.75]	28.4 [1.12]	1.78 [07]	2.03 [08]	0.61 [024]	82.8 [3.26]
202C663	22.5 [57.2]	77.2 [3.04]	40.6 [1.60]	57.2 [2.25]	54.6 [2.15]	22.9 [90]	62.2 [2.45]	236.2 [9.30]	35.1 [1.38]	2.03 [08]	2.03 [08]	0.66 [026]	138.4 [5.45]

Note: Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5 [.06] max.

VITON is a trademark of DuPont
Performance Elastomers

Available in:	Americas	Europe	Asia Pacific
	■	■	■