


RC Standard marker cards (cont.)

Horizontal marking of numbers (cont.)

1	2	3	4	5	6	7	8	9	10
11	12	13	14	15	16	17	18	19	20
21	22	23	24	25	26	27	28	29	30



For vertical markers, see page 1933.

Horizontal marking
Increasing order

RCAL85
1 → 100 **0237 030.22**
See page 1936.

RC55	RC510	RC65	RC610	RC810	RC1010
1 → 100 0230 030.07	1 → 100 0231 030.24	1 → 100 0232 030.25	1 → 100 0233 030.26	1 → 100 0234 030.27	1 → 80 0238 030.03
101 → 200 0230 031.24	101 → 200 0231 031.11	101 → 200 0232 031.12	101 → 200 0233 031.13	101 → 200 0234 031.14	81 → 160 0238 031.20
201 → 300 0230 032.25	201 → 300 0231 032.12	201 → 300 0232 032.13	201 → 300 0233 032.14	201 → 300 0234 032.15	161 → 240 0238 032.21
301 → 400 0230 033.26	301 → 400 0231 033.13	301 → 400 0232 033.14	301 → 400 0233 033.15	301 → 400 0234 033.16	241 → 320 0238 033.22
401 → 500 0230 034.34	401 → 500 0231 034.14	401 → 500 0232 034.15	401 → 500 0233 034.16	401 → 500 0234 034.17	321 → 400 0238 034.23
501 → 600 0230 035.20	501 → 600 0231 035.15	501 → 600 0232 035.16	501 → 600 0233 035.17	501 → 600 0234 035.10	401 → 480 0238 035.24
601 → 700 0230 036.21	601 → 700 0231 036.16	601 → 700 0232 036.17	601 → 700 0233 036.10	601 → 700 0234 036.11	481 → 560 0238 036.25
701 → 800 0230 037.22	701 → 800 0231 037.17	701 → 800 0232 037.10	701 → 800 0233 074.26	701 → 800 0234 037.12	561 → 640 0238 037.26
801 → 900 0230 038.03	801 → 900 0231 038.20	801 → 900 0232 038.21	801 → 900 0233 075.27	801 → 900 0234 038.23	641 → 720 0238 038.07
901 → 1000 0230 039.04	901 → 1000 0231 039.21	901 → 1000 0232 039.22	901 → 1000 0233 076.20	901 → 1000 0234 039.24	721 → 800 0238 039.00
1001 → ... 0230 071.04*	1001 → ... 0231 071.21*	1001 → ... 0232 071.22*	1001 → ... 0233 073.25*	1001 → ... 0234 071.24*	801 → 880 0238 040.15
					881 → 960 0238 041.02

* Part numbers identical for each group of numbers : on request (indicate marking). Ex. : 0230 071.04 : 1001 to 1100.

8	8	8	8	8	8	8	8	8	8
8	8	8	8	8	8	8	8	8	8
8	8	8	8	8	8	8	8	8	8

Horizontal marking
Repeated identical numbers

Markers	Marking method	Marker width mm	Marker height, L mm	Use with terminal blocks thickness
RC55	⑤ ⑩	5	5	5 mm
RC510	⑥ ⑩	5	10	5 mm
RC65	⑤ ⑪	6	5	6 mm
RC610	⑥ ⑪	6	10	6 mm
RC810	⑰	8	10	8 mm
RC1010	⑳	10	10	10 mm and larger

RC55	RC510	RC65	RC610
100 x 0 0230 240.26	100 x 0 0231 210.05	100 x 0 0232 201.02	100 x 0 0233 201.03
100 x 1 0230 241.13	100 x 1 0231 211.22	100 x 1 0232 202.03	100 x 1 0233 202.04
100 x 2 0230 242.14	100 x 2 0231 212.23	100 x 2 0232 203.04	100 x 2 0233 203.05
100 x 3 0230 243.15	100 x 3 0231 213.24	100 x 3 0232 204.05	100 x 3 0233 204.06
100 x 4 0230 244.16	100 x 4 0231 214.25	100 x 4 0232 205.06	100 x 4 0233 205.07
100 x 5 0230 245.17	100 x 5 0231 215.26	100 x 5 0232 206.07	100 x 5 0233 206.00
100 x6 or 9 0230 246.10	100 x6 or 9 0231 216.27	100 x6 or 9 0232 207.00	100 x6 or 9 0233 207.01
100 x 7 0230 247.11	100 x 7 0231 217.20	100 x 7 0232 208.11	100 x 7 0233 208.12
100 x 8 0230 248.22	100 x 8 0231 218.01	100 x 8 0232 209.12	100 x 8 0233 209.13
100 x 10 0230 250.20	100 x 10 0231 220.07	100 x 10 0232 211.23	100 x 10 0233 211.24
100 x 11 0230 251.15	100 x 11 0231 221.24	100 x 11 0232 212.24	100 x 11 0233 212.25
100 x 12 0230 252.16	100 x 12 0231 222.25	100 x 12 0232 213.25	100 x 12 0233 213.26
100 x 13 0230 253.17	100 x 13 0231 223.26	100 x 13 0232 214.26	100 x 13 0233 214.27
100 x 14 0230 254.10	100 x 14 0231 224.27	100 x 14 0232 215.27	100 x 14 0233 215.20
100 x 15 0230 255.11	100 x 15 0231 225.20	100 x 15 0232 216.20	100 x 15 0233 216.21
100 x 16 0230 256.12	100 x 16 0231 226.21	100 x 16 0232 217.21	100 x 16 0233 217.22
100 x 17 0230 257.13	100 x 17 0231 227.22	100 x 17 0232 218.02	100 x 17 0233 218.03
100 x 18 0230 258.24	100 x 18 0231 228.03	100 x 18 0232 219.03	100 x 18 0233 219.04
100 x 19 0230 259.25	100 x 19 0231 229.04	100 x 19 0232 220.00	100 x 19 0233 220.01
100 x 20 0230 260.22	100 x 20 0231 230.01	100 x 20 0232 221.25	100 x 20 0233 221.26
	100 x .. } 0231 231.26*	100 x .. } 0232 222.26*	100 x .. } 0233 222.27*
	999	999	999

* Part numbers identical for each group of numbers : on request (indicate marking). Ex. : 0231 231.26 : 100 x 21.