

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


51067-0300

Status:

Active

Description:

3.50mm Pitch Wire-to-Wire and Wire-to-Board Housing, Positive Lock, 3 Circuits



Documents:

- 3D Model

Drawing (PDF)

Product Specification PS-51067-001 (PDF)

Product Specification PS-51067-002 (PDF)

Product Specification PS-51067-003 (PDF)

Product Specification PS-51067-004 (PDF)

Product Specification PS-51067-005 (PDF)

Product Specification PS-51067-006 (PDF)

Product Specification PS-51067-007 (PDF)

Product Specification PS-51067-008 (PDF)
- Product Specification PS-51067-016 (PDF)

Product Specification PS-51067-017 (PDF)

Product Specification PS-51067-018 (PDF)

Product Specification PS-51067-019 (PDF)

Product Specification PS-51067-021 (PDF)

Product Specification PS-51067-022 (PDF)

Product Specification PS-54111-001 (PDF)

Product Specification PS-54452-006 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
TUV	R72081037
UL	E29179

General

Product Family	Crimp Housings
Series	51067
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	N/A
UPC	800753574373

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	694.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Reference - Drawing Numbers

Product Specification	PS-51067-001, PS-51067-002, PS-51067-003, PS-51067-004, PS-51067-005, PS-51067-006, PS-51067-007, PS-51067-008, PS-51067-016, PS-51067-017, PS-51067-018, PS-51067-019, PS-51067-021, PS-51067-022, PS-54111-001, PS-54452-006, RPS-51067-001, RPS-51067-002, RPS-51067-003, RPS-51067-006, RPS-51067-007, RPS-51067-008, RPS-51067-014, RPS-51067-020, RPS-51067-021, RPS-51067-022, RPS-51067-024, RPS-51067-025, RPS-51067-027, RPS-51067-028, RPS-51067-029, RPS-51067-030, RPS-51067-034,
-----------------------	--

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

51067Series

Mates With

51114 , 53258 , 53259 , 53265 , 53266

Use With

50217 Crimp Terminals

RPS-51067-035, RPS-51067-036, RPS-51067-037,
RPS-51067-041, RPS-51067-043
SD-51067-**-00

This document was generated on 02/27/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION