

Label sheet, DIN A4 - BMKL 64X34 WH - 5032400

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, Sheet, white, unlabeled, can be labeled with: Office printing systems, Mounting type: Adhesive, Lettering field: 64 x 34 mm




The figure shows a version of the article

Why buy this product

- These labels have been specially developed for laser printers
- The unperforated SK U ... sheets are available for custom label designs
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".
- Can be printed on all commercially available laser printers



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 095796 |
| Weight per Piece (excluding packing) | 0.14 g |
| Custom tariff number | 39199000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 34 mm |
| Width (a) | 64 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 80 °C |
|---------------------------------|------------------|

General

| | |
|------|---|
| Note | Print image may vary depending on laser printer |
|------|---|

Label sheet, DIN A4 - BMKL 64X34 WH - 5032400

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Color | white |
| Base element material | Polyester |
| Components | Silicone-free |
| Material | Polyester |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 21 |
| Number of individual labels per row | 3 |
| Marking mounting type | Adhesive |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190218 |
| eCl@ss 4.1 | 24190218 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Accessories

Accessories

Printing system accessories

Label sheet, DIN A4 - BMKL 64X34 WH - 5032400

Accessories

Accessories - CMS-P1-PAD - 5144819



Accessories

Drawings

Dimensioned drawing

