

WARRANTY

NightSearcher products have been carefully tested and inspected before shipment and are guaranteed to be free from defective materials and workmanship for a period of 12 months from the date of purchase, provided that the enclosed instructions have been followed.

Should you experience problems with your NightSearcher product, please return the item, complete with any chargers, to your place of purchase or contact NightSearcher Ltd direct.

Address and contact details;

NightSearcher Limited

Unit 4 Applied House
Fitzherbert Spur
Farlington
PORTSMOUTH
Hampshire
PO6 1TT
UK

T: +44 (0)23 9238 9774 | E: sales@nightsearcher.co.uk

If upon inspection it is found that the fault occurring is due to defective materials or workmanship, repairs will be carried out free of charge. This guarantee does not apply to normal wear and tear, nor does it cover any damage caused by misuse, careless / unsafe handling, alterations, accidents, or repairs attempted or made by any personnel without prior approval from NightSearcher Ltd.

Batteries are consumable items and are not covered by this guarantee. Your guarantee is not effective unless you can produce a dated receipt of purchase.

Please note that this guarantee does not affect your statutory rights.

Safe disposal of waste electrical products, batteries and bulbs

If at any time, you need to dispose of this product or parts of this product: please note that waste electrical products, bulbs and batteries should not be disposed of with ordinary household waste. Recycle where facilities exist. Check with your local authority for recycling advice. **Alternatively, NightSearcher is happy to take receipt of this product at end-of-life and will recycle it on your behalf.**



NIGHTSEARCHER

NightSearcher Power-Star ★

Super Bright Rechargeable 3W LED Torch
with Built-In Mobile Device Charger



USER MANUAL

NIGHTSEARCHER LIMITED

Unit 4 Applied House, Fitzherbert Spur, Farlington
Portsmouth, Hampshire, PO6 1TT, UK

T: +44 (0)23 9238 9774 | F: +44 (0)23 9238 9788

E: sales@nightsearcher.co.uk | www.nightsearcher.co.uk

Please read this User Manual before using your NightSearcher product, as it contains important safety information and operating instructions. Following this advice will help ensure that your product operates to its maximum potential.

TECHNICAL SPECIFICATION

Light output	180 lumens
Light source	3W Cree® XR-E Q5 LED
Run time (hours)	10 28
Charge time (hours)	7 to 9
Battery	5500mAh Lithium Ion Rechargeable
Input (Micro USB) :	5V / 1A (max)
Output (USB Type A)	5V / 2.1A (max)
Product size (mm)	L129 x W48 x H48
Product weight (kg)	0.1565
Part No	NSPOWERSTAR

Supplied with: USB charging / data cable

LED ASSEMBLY REPLACEMENT

The Light Emitting Diodes (LEDs) can last over 50,000 hours and seldom need replacing. If the LED should malfunction, please contact NightSearcher Limited or an authorised distributor.

TO CHARGE THE NIGHTSEARCHER POWERSTAR ★

NOTE: Fully charge before using your NightSearcher Power-Star ★ for the first time.

It is important to connect the charger as described below

- Using the supplied USB charging cable select the mini USB connector and insert it into the input socket (1)
- Plug the USB plug into any USB output socket
- When charging voltage is detected the battery status indicators will illuminate to show charge status
- The **NightSearcher Power-Star ★** will take between 7 and 9 hours to fully recharge from flat.
- When fully charged all status LEDs will illuminate steady

TO CHARGE YOUR MOBILE DEVICE

- Using the supplied USB cable, connect to the USB output socket (4) on the base of the unit
- Connect the other end of the lead to your mobile device ensuring to select the correct connector
- Your device will indicate charging; the battery status indicators on the **NightSearcher Power-Star ★** will light up one by one to show battery capacity

BATTERY LEVEL INDICATOR

- Press power switch (2), the LED indicator(s) turn(s) on to show the battery capacity
- The LED indicator(s) turn(s) off after 10 seconds

TO USE THE TORCH

- Press and turn on power switch (2), then press the torch on/off switch (3) to turn on the LED light.
- Multimode switch cycles between: standard brightness → high brightness → emergency blinking light → SOS distress signal light → power off

MAINTENANCE

- To assure product SAFETY and RELIABILITY, all repairs, maintenance and adjustment should be performed by NightSearcher Ltd or an authorised

Distributor.

- Make sure the torch is completely dry before use
- When the unit is excessively discharged, or the connected device is not stable, its protection circuit will automatically de-activate the unit
- To re-activate the unit, unplug the connected device and short charge the unit

SAFETY PRECAUTIONS

- Do not allow children to play with the torch
- Do not shine directly into eyes
- Do not expose the battery to fire/high temperatures or extreme wet/cold conditions
- Do not try to repair the unit or adaptor yourself. Please contact NightSearcher Ltd or an authorised Distributor
- Do not use excessive force on the product as this may cause permanent damage to the unit
- Always keep the unit fully charged when not in use
- It is important to recharge the unit as soon as possible after each usage
- The Li-ion rechargeable battery in this unit must be recycled or disposed of properly

