



RECOMMENDED LAYOUT FOR
.062 THICK P.C BOARD

- PARTS COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3
- CONTACT IS PLATED OVERALL WITH .000050 NICKEL, THEN .000030 GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.

| | | | | |
|---|--|----|----|--------|
| N | OBsolete 2-1-1 PER ECN CM-2706 | NG | RS | 8-9-92 |
| M | REACTIVATE 2-1-1 TTI CM 86-11 | KJ | RS | 4-2-86 |
| L | OBsolete 4-17-74 2-2-343-2-41-4-3 5-1-6-1-6-2-7-4 7-2-8-1-8-2-9-4 9-2 CM 473 | KJ | RS | 4-2-86 |

| | | | |
|----|-------------------------|----|------------|
| KJ | RESTORED | RS | 4/86 |
| K | REV. PER M-7375 | 53 | QM 8/27/83 |
| J | 496 was 180 M-7285 | 45 | DM 7/1/83 |
| H | ADDED NOTE 2, M-6674 | 45 | DM 1/25/84 |
| G | REMOVED SOLDER M-6583 | 45 | DM 8-17-81 |
| F | ADDED CHANGE M-5934 | 45 | DM 7-11-82 |
| E | REV. 707 LEAD 27 M-5334 | 45 | DM 5-21-79 |
| D | REVISED M-3932 | 45 | DM 5-23-77 |
| C | ECN M-3671 | 45 | DM 1/28/84 |
| B | ECN M-3452 | 45 | DM 8/26/83 |
| A | ECN M-3152 | 45 | DM 7/20/82 |

Unpublished copy not to be reproduced nor published without written permission of AMP Incorporated

| | |
|-----------------------|--------|
| NUMBER | 350543 |
| REQUIRED PER ASSEMBLY | |
| DESCRIPTION | |

| | | |
|-----|---------|-----------|
| DR | 3-30-73 | 9. Edmund |
| CHK | 4/1/73 | cm Albin |
| DE | 4-10-73 | Thomson |
| DR | 3-30-73 | 9. Edmund |
| CHK | 4/1/73 | cm Albin |
| DE | 4-10-73 | Thomson |

| | | |
|--------------|-------------------|----------------------|
| 350543-1 | NYLON - NATURAL | Copper Alloy PRE-TIN |
| 350543-2 | NYLON - NATURAL | Copper Alloy - GOLD |
| 5-350543-2 | NYLON - GREEN | COPPER ALLOY-GOLD |
| ASSEMBLY NO. | HSG. MATL & COLOR | PIN MATL & FINISH |

| | |
|-------|---------------------------------------|
| CLASS | CB4 DIA. PIN |
| TYPE | POSITIVE LOCK |
| LOC | B |
| NO | 350543 |
| REV | N |
| NAME | 4 CIRCUIT MATE-N-10K P.C BOARD HEADER |

