

FAZ Miniature Circuit-Breakers


Switching Capacity 10 kA (IEC/EN 60 898)

MCB Enclosures, Fuse Enclosures

		1-pole				2-pole With 2 protected poles				3-pole With 3 protected poles		
												
Characteristic	Rated current	Type	Article no.	Price	Std. pack	Type	Article no.	Price	Type	Article no.	Price	
	I_n A			See Price List				See Price List			See Price List	
FAZ miniature circuit-breakers												
B Response current of short-circuit release $3 - 5 \times I_n$	4	FAZ-B4HI 214570			12 off	FAZ-2-B4HI 214571			--			
	6	FAZ-B6 211352				FAZ-2-B6 211353			FAZ-3-B6 211354			
	10	FAZ-B10 211358				FAZ-2-B10 211359			FAZ-3-B10 211360			
	13	FAZ-B13 211364				FAZ-2-B13 211365			FAZ-3-B13 211366			
	16	FAZ-B16 211370				FAZ-2-B16 211371			FAZ-3-B16 211372			
	20	FAZ-B20 211376				FAZ-2-B20 211377			FAZ-3-B20 211378			
	25	FAZ-B25 211382				FAZ-2-B25 211383			FAZ-3-B25 211384			
	32	FAZ-B32 211388				FAZ-2-B32 211389			FAZ-3-B32 211390			
	40	FAZ-B40 211394				FAZ-2-B40 211395			FAZ-3-B40 211396			
	50	FAZ-B50 211400				FAZ-2-B50 211401			FAZ-3-B50 211402			
	63	FAZ-B63 211406				FAZ-2-B63 211407			FAZ-3-B63 211408			
C Response current of short-circuit release $5 - 10 \times I_n$	0.5	FAZ-C0,5 211474			12 off	FAZ-2-C0,5 211475			FAZ-3-C0,5 211476			
	1	FAZ-C1 211480				FAZ-2-C1 211481			FAZ-3-C1 211482			
	2	FAZ-C2 211486				FAZ-2-C2 211487			FAZ-3-C2 211488			
	3	FAZ-C3 211492				FAZ-2-C3 211493			FAZ-3-C3 211494			
	4	FAZ-C4 211498				FAZ-2-C4 211499			FAZ-3-C4 211500			
	6	FAZ-C6 211504				FAZ-2-C6 211505			FAZ-3-C6 211506			
	10	FAZ-C10 211510				FAZ-2-C10 211511			FAZ-3-C10 211512			
	13	FAZ-C13 211516				FAZ-2-C13 211517			FAZ-3-C13 211518			
	16	FAZ-C16 211522				FAZ-2-C16 211523			FAZ-3-C16 211524			
	20	FAZ-C20 211528				FAZ-2-C20 211529			FAZ-3-C20 211530			
	25	FAZ-C25 211534				FAZ-2-C25 211535			FAZ-3-C25 211536			
	32	FAZ-C32 211540				FAZ-2-C32 211541			FAZ-3-C32 211542			
	40	FAZ-C40 211546				FAZ-2-C40 211547			FAZ-3-C40 211548			
	50	FAZ-C50 211552				FAZ-2-C50 211553			FAZ-3-C50 211554			
	63	FAZ-C63 211558				FAZ-2-C63 211559			FAZ-3-C63 211560			

FAZ Miniature Circuit-Breakers

Switching Capacity 10 kA (IEC/EN 60 898)

4-pole With 4 protected poles		2-pole With 1 protected pole N switching with pole		4-pole With 3 protected poles N switching with poles		Notes
Type	Price	Type	Price	Type	Price	
Article no.	See Price List	Article no.	See Price List	Article no.	See Price List	Std. pack
						
FAZ-4-B6 211355		FAZ-1N-B6 211356		FAZ-3N-B6 211357		1 off
FAZ-4-B10 211361		FAZ-1N-B10 211362		FAZ-3N-B10 211363		Switching capacity (IEC/EN 60 947-2) 10 kA
FAZ-4-B13 211367		FAZ-1N-B13 211368		FAZ-3N-B13 211369		Switching capacity (IEC/EN 60 947-2) 15 kA
FAZ-4-B16 211373		FAZ-1N-B16 211374		FAZ-3N-B16 211375		Accessories
FAZ-4-B20 211379		FAZ-1N-B20 211380		FAZ-3N-B20 211381		Auxiliary contacts, 12/015
FAZ-4-B25 211385		FAZ-1N-B25 211386		FAZ-3N-B25 211387		Voltage releases 12/015
FAZ-4-B32 211391		FAZ-1N-B32 211392		FAZ-3N-B32 211393		Mounting accessories 12/019
FAZ-4-B40 211397		FAZ-1N-B40 211398		FAZ-3N-B40 211399		Maximum mounting options 12/045
FAZ-4-B50 211403		FAZ-1N-B50 211404		FAZ-3N-B50 211405		FAZ-B4HI, FAZ-2-B4HI
FAZ-4-B63 211409		FAZ-1N-B63 211410		FAZ-3N-B63 211411		Special miniature circuit-breakers with drastically reduced let-through energy to prevent contact welding in auxiliary contact modules
FAZ-4-C0,5 211477		FAZ-1N-C0,5 211478		FAZ-3N-C0,5 211479		1-pole
FAZ-4-C1 211483		FAZ-1N-C1 211484		FAZ-3N-C1 211485		Depth 71 mm
FAZ-4-C2 211489		FAZ-1N-C2 211490		FAZ-3N-C2 211491		Width 17.5 mm
FAZ-4-C3 211495		FAZ-1N-C3 211496		FAZ-3N-C3 211497		
FAZ-4-C4 211501		FAZ-1N-C4 211502		FAZ-3N-C4 211503		2-pole; 1-pole+N
FAZ-4-C6 211507		FAZ-1N-C6 211508		FAZ-3N-C6 211509		Depth 71 mm
FAZ-4-C10 211513		FAZ-1N-C10 211514		FAZ-3N-C10 211515		Width 35 mm
FAZ-4-C13 211519		FAZ-1N-C13 211520		FAZ-3N-C13 211521		
FAZ-4-C16 211525		FAZ-1N-C16 211526		FAZ-3N-C16 211527		3-pole
FAZ-4-C20 211531		FAZ-1N-C20 211532		FAZ-3N-C20 211533		Depth 71 mm
FAZ-4-C25 211537		FAZ-1N-C25 211538		FAZ-3N-C25 211539		Width 52,5 mm
FAZ-4-C32 211543		FAZ-1N-C32 211544		FAZ-3N-C32 211545		
FAZ-4-C40 211549		FAZ-1N-C40 211550		FAZ-3N-C40 211551		4-pole; 3-pole+N
FAZ-4-C50 211555		FAZ-1N-C50 211556		FAZ-3N-C50 211557		Depth 71 mm
FAZ-4-C63 211561		FAZ-1N-C63 211562		FAZ-3N-C63 211563		Width 70 mm
						