

Project..... **Comments**.....

Fixture Type..... **Prepared By**.....

Product Description:

Rotatable end caps
 SMD LEDs
 High colour rendering index (Ra)80
 360° Impact resistant frosted polycarbonate tube covers the aluminium heatsink
 Starter allows for safe lamp replacement (starter included)
 High power factor >0.90
 Suitable for use at -30° to +45°C
 1kV surge protection
 Beam 130°
 Non-dimmable
 Voltage range 100-240V
 Life to 70% lumen maintenance (L70) - 30,000 hours
 4 Year Warranty - see www.auroralighting.com for details

Product Image:



Product Features:

- Rotatable end caps
- SMD LEDs
- High colour rendering index (Ra)80
- 360° Impact resistant frosted polycarbonate tube covers the aluminium heatsink
- LED Starter allows for safe lamp replacement (starter included)
- High power factor >0.90
- Suitable for use at -20° to +45°C
- 1kV surge protection
- Beam 130°
- Non-dimmable
- Voltage range 100-240V
- Life to 70% lumen maintenance (L70) - 30,000 hours
- 4 Year Warranty - see www.auroralighting.com for details

Product Specs:

Input Voltage	100~240V AC
Input Frequency	50/60Hz
Power Factor	0.9
Operating Temp (Min-Max)	-30-45°C
Dimmable	No
Dimensions	1498mm (OL)
Number of LEDs	243

Compliance & Approvals:



SKU Table and Ordering

Cat. No.	Diffuser	Color	Im	Wattage	Lumens/Watt	Quantity
AU-XT81527FRB/65	Frosted	6500K	2200lm	26W	84.62	
AU-XT81527FRB/40	Frosted	4000K	2200lm	26W	84.62	

Warranty:

This product has a warranty period of 4 Years from the date of purchase. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Sales

16 Alban Park Hatfield Road
 St. Albans AL4 0JJ
 United Kingdom
 Tel : +44 (0) 1727 83 66 11
 Fax : +44 (0) 1727 83 66 22

UK Distribution

Apex Park 6 Little Burrow
 Welwyn Garden City AL7
 4SW
 United Kingdom
 Tel : +44 (0) 1707 35 18 20
 Fax : +44 (0) 1727 35 18 21