

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19215-0037](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Step Down Butt Splice for 8-12 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series [19215](#)  
 Comments Step down: 8 to 10/12 AWG  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Splices](#)  
 Product Name Butt - Step Down  
 UPC 800755062571

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 4.705/g  
 Packaging Type Bag  
 Temperature Range - Operating 149°C  
 Wire Insulation Diameter N/A  
 Wire Size AWG 10, 2, 8  
 Wire Size mm<sup>2</sup> N/A

**Material Info**

Old Part Number DC-354

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19215-004



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

19215Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

| Description   | Product #                  |
|---|----------------------------|
| RHT1080 Hand Crimp Tool                             | <a href="#">0640034400</a> |
| Crimp Head for the AT-200™ Pneumatic Hand Tool      | <a href="#">0640074400</a> |
| Hand Crimp Tool                                     | <a href="#">0640013900</a> |
| Putt Pump Dieless Head System                       | <a href="#">0192860065</a> |
| Manual Putt Pump Hydraulic System, Die set required | <a href="#">0192860117</a> |
| Square "DIN" style dies for 8 AWG                   | <a href="#">0640037670</a> |

Die Set (large) for 0192900001  
the HHLS Hydraulic  
Crimper

This document was generated on 10/03/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**