

Customer Information Sheet

DRAWING No.: M80-542XXXX

SHEET 2 OF 2





IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**SPECIFICATIONS:****MATERIAL:**

MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK

CONTACT = BRASS

JACKSCREW = STAINLESS STEEL

FINISH:22 = 0.75µ GOLD ON CONTACT AREA,
0.3µ 90/10 TIN/LEAD ON TAILS42 = 0.75µ GOLD ON CONTACT AREA,
0.3µ 100% TIN ON TAILS**ELECTRICAL:**

CURRENT RATING AT 25°C = 3.0A MAX

CURRENT RATING AT 85°C = 2.2A MAX

WORKING VOLTAGE = 120V AC/DC

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE = 25 mΩ MAX


INSULATION RESISTANCE = 100 MΩ MIN

MECHANICAL:

DURABILITY = 500 OPERATIONS

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING: TUBEFOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C005XX (LATEST ISSUE)**ORDER CODE:****M80-542XXXX****No. OF CONTACTS**06, 10, 12, 14, 18, 20
22, 26, 34, 42, 44, 50**FINISH**22 - GOLD, 90/10 TIN/LEAD
42 - GOLD, 100% TIN

ASSY PART No.	No. CONTACTS	DIM 'A'	DIM 'B'	DIM 'C'
M80-54206XX	6	4.00	11.00	16.00
M80-54210XX	10	8.00	15.00	20.00
M80-54212XX	12	10.00	17.00	22.00
M80-54214XX	14	12.00	19.00	24.00
M80-54218XX	18	16.00	23.00	28.00
M80-54220XX	20	18.00	25.00	30.00
M80-54222XX	22	20.00	27.00	32.00
M80-54226XX	26	24.00	31.00	36.00
M80-54234XX	34	32.00	39.00	44.00
M80-54242XX	42	40.00	47.00	52.00
M80-54244XX	44	42.00	49.00	54.00
M80-54250XX	50	48.00	55.00	60.00

JMB	2	21.12.06	9626
NAME	ISS.	DATE	C/NOTE
APPROVED: JMB			
CHECKED: JMB			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCESX. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²TITLE: JACKSCREW DATAMATE
DIL HORIZONTAL SMT MALE
ASSEMBLY (BOARD MOUNT)

DRAWING NUMBER:

M80-542XXXXSHT
2 OF 2

HARWIN INC U.S.A. TEL: (812) 542 2540 FAX: (812) 542 2541	HARWIN PLC U.K. TEL: 023 9231 4545 FAX: 023 9231 4590	HARWIN PTE SINGAPORE TEL: 65 6779 4909 FAX: 65 6779 3868
--	--	---