

# TECHNICAL SPECIFICATION



## EVO®2 Mid Peak OneTouch™ Slip Ratchet Vented

White / AJF030-000-100



### DESCRIPTION

The EVO®2 Comfort Plus helmet combines a super strong shell for superior all day protection in the widest range of environments, with the comfort benefits of the new Evolution® 3D Adjustment™ harness system. EVO®2 is a true evolution of the long-established MK®2 and MK®3 helmets. The EVO®2 retains the JSP signature styling while incorporating developments first seen in the EVO®8. Packed full of the latest protection technology and features.

### OPTIONS

- White (AJF030-000-100)**
- Blue (AJF030-000-500)
- Black (AJF030-001-100)
- Orange (AJF030-000-800)
- Green (AJF030-000-300)
- Grey - AJF030-000-400 - Made To Order Min 240 units (AJF030-000-400)
- Yellow (AJF030-000-200)
- Pink (AJF030-003-900)
- Red (AJF030-000-600)

### SAFETY STANDARDS

EN 397



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.


















Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jsp-safety.com / Web: www.jsp-safety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jsp-safety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 3 / Issued 31 Oct 2022 / Copyright 2018 - 2022. JSP Limited. All Rights Reserved.



## SPECIFICATIONS

|  |                                   |   |                                |
|--|-----------------------------------|---|--------------------------------|
|  | Peak<br>Mid                       |  | Impact Resistance<br>50 Joules |
|  | Molten Metal<br>Yes               |  | Maximum Temperature<br>+50°C   |
|  | Minimum Temperature<br>-30°C      |  | HDPE Shell<br>Yes              |
|  | Recyclable<br>Shell               |  | LDPE Harness<br>Yes            |
|  | Depth Adjustment<br>3D Harness    |  | Slip Ratchet<br>Slip           |
|  | Universal Accessories Slot<br>Yes |  | Ventilation<br>Yes             |
|  | BSI Kitemark<br>Yes               |  | Reflective Option<br>Optional  |
|  | ID card holder<br>Optional        |  | JSPCheck<br>Yes                |
|  | Product Weight<br>402g            |   |                                |

## FEATURES



### Firmest Fit Available

The deep nape strap enables the firmest retention of any helmet, keeping it firmly rooted on the head. The OneTouch™ slip ratchet makes it simple to tighten to the perfect fit.



### CR2 Reflective

Using Class RA2, high intensity reflective. CR2 is the biggest step-up in night time visibility/reflectivity of head protection to date. Conforms to Class RA2, EN12899-1.



### Supreme Comfort

A traditional 6-point polyethylene harness making the EVO@2 the more economical choice, whilst still providing the same high performance as the EVO@3.



### Ventilation Option

Side and rear ventilation for optimum air movement inside the shell, reducing helmet temperatures by an average 2-3 degrees.



### 3D Adjustment

The polyethylene harness features unique 1-2-3 point depth settings. This offers the most precise fit attainable on an industrial safety helmet.



### Accessories

A universal attachment slot enables firm fitting of a range of Surefit™ safety visors and ear defenders.



### JSP Logo Express®

Strengthen your corporate identity by applying a company logo on a range of our safety helmets. Minimum order quantities and set-up charges apply.

## LOGO

- Front
- Back

## RANGE



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jsspsafety.com / Web: www.jsspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jsspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 3 / Issued 31 Oct 2022 / Copyright 2018 - 2022. JSP Limited. All Rights Reserved.





VIDEOS

[www.youtube.com/watch?v=n9qrN2U0LFk](https://www.youtube.com/watch?v=n9qrN2U0LFk)

DOWNLOADS

 [Image Pack \(ZIP\)](#)

 [doc-invincible-evo2.pdf \(PDF\)](#)



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: [sales@jgpsafety.com](mailto:sales@jgpsafety.com) / Web: [www.jgpsafety.com](http://www.jgpsafety.com)

Do Not Publish without written permission from JSP Limited. Contact [copyright@jgpsafety.com](mailto:copyright@jgpsafety.com). Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 3 of 3 / Issued 31 Oct 2022 / Copyright 2018 - 2022. JSP Limited. All Rights Reserved.

