

GEOCHEM

WATER RESISTANT WOOD ADHESIVE

HIGH QUALITY RESIN BASED WOOD ADHESIVE

Geochem Water Resistant Wood Adhesive is a high quality resin based wood adhesive suitable for all general uses in woodworking and joinery applications. It can be used internally and externally and provides a high strength, impact resistant bond that is usually stronger than wood itself.

Geochem Water Resistant Wood Adhesive is ideal for all wood to wood bonding e.g. window frames, door frames, furniture assembly, DIY and household use. It dries to a clear finish that can be sanded, painted or stained. Full bond strength will be achieved in 24 hours.

Geochem Water Resistant Wood Adhesive:


- For internal and external use
- High strength wood to wood bonding
- Suitable for most woods
- Dries clear – easy clean up
- Quick drying
- Water resistant for short term contact with water or high humidity situations, such as kitchens, bathrooms and window frames

SPECIFICATIONS

Conforms to EN 204 Type D3



PROFESSIONAL
BUILDING
CHEMICAL
RANGE



TECHNICAL DATA

Form	Liquid
Storage Life	12 Months stored between 5°C and 25°C in original containers

Specification writers: These values are not intended for use in preparing specifications. Please contact your local **Geocel® Sales Representative** prior to writing specifications on this product.

SURFACE PREPARATION

Ensure surfaces are dust free and uncontaminated. Clean oily woods such as teak with white spirit before bonding. If the surface has been damaged by planing or sawing, use a medium grade sandpaper to abrade the surface.

APPLICATION

Apply adhesive evenly to one surface only. Assemble the parts to be bonded while the adhesive is still wet. Put in any nails or screws used in the assembly before applying light pressure to the bond using a vice, clamp or weights. Press the two surfaces together and clamp for 3-4 hours.

The open or working time for the assembly varies depending on the moisture content of the wood and ambient conditions. Generally this will be around 10 -25 minutes.

Clean off excess adhesive with a damp cloth.

Dries clear in 24 hours

COVERAGE

For timber bonding and laminating, coverage is typically 10m² per litre.

CLEANING

Clean all equipment with soap and water immediately after use.

PACKAGING

Geocem Water Resistant Wood Adhesive is available in 500ml, 1 Litre, 2.5 Litre and 5 Litre bottles.

LIMITATIONS

Not suitable for continuous immersion in water.

HEALTH AND SAFETY

Geocem Water Resistant Wood Adhesive is classified as non hazardous. For further information please refer to Health and Safety data sheets available on request.

TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and Safety information, contact **Geocel® Technical Service**.

IMPORTANT NOTE The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Geocel's products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Geocel's sole warranty is that the product will meet the Geocel sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

Geocel specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability.

Geocel disclaims liability for any incidental or consequential damages.

Geocel®

Geocel Limited

Western Wood Way, Langage Science Park, Plympton, Plymouth, Devon, PL7 5BG

Tel: 01752 334350 Fax: 01752 202065 Email: info@geocel.co.uk

www.geocel.co.uk