

General Information

Extended Product Type:	BJMI5-4
Product ID:	1SNA176280R0500
EAN:	3472591762808
Catalog Description:	BJMI5-4 POLES Jumper Bars
Long Description:	- IP20 assembled screw jumper bars, - Fractionnable model with captive screws and spacer s, - Allows connection between consecutive blocks only.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C
Color:	Grey
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Declaration of Conformity - CE:	1SND225001C1009
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAN:	3472591762808
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
Insulation Material:	Polyamide
Invoice Description:	BJMI5-4 POLES Jumper Bars
Minimum Order Quantity:	10 piece
Mounting Type:	Fractionnable model, composed of captive screws on a jumper bar, with IP20 protection touchproof. This accessory can be used for connecting consecutive blocks only.
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Object Classification Code:	X
Order Multiple:	10 piece
Package Level 1 EAN:	3472591762808
Package Level 1 Gross Weight:	0.067 kg
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 2 Units:	1000 piece
Package Level 3 Units:	48000 piece
Product Main Type:	BJMI
Product Name:	Jumper Bar
Product Net Depth:	5 mm
Product Net Height:	20.6 mm

Product Net Weight:	6.7 g
Product Net Width:	5 mm
Product Packing Type:	Bag
Rated Current (I _n):	Main Circuit 24 A
RoHS Information:	1SND230492F0201
Selling Unit of Measure:	piece
Spacing:	5 mm
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw
Suitable For:	D1.5/5.ADO.NF D1/5.ADO D1/5.D2.ADO D2.5/5.ADO D2.5/5.D2.ADO MA2.5/5 MA2.5/5-2CPE MA2.5/5-CPE MA2.5/5D-2CPE

