

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130064-0187](#)  
**Status:** **Active**  
**Overview:** Brad® Quick-Change® Connectors  
**Description:** Quick-Change® Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 10 AWG, PVC Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family	Industrial Cordsets
Series	<a href="#">130064</a>
Connector End A	Quick-Change®
Connector End B	Quick-Change®
IP Rating	IP67
Overview	<a href="#">Brad® Quick-Change® Connectors</a>
Product Name	Quick-Change®
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	78678855746

**Physical**

Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold over Nickel
Net Weight	105.910/g
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	10
Wire/Cable Type	STOOW, TC-ER Direct Burial

**Electrical**


Current - Maximum per Contact	25A
Voltage - Maximum	600V

**Material Info**

Old Part Number	CC4030A48M020
-----------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-130064-005, SD-130064-065
---------------	------------------------------



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

130064Series

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**