

OPERATOR PANEL;
 INSTALLATION INTO CONTROL CABINET DOOR OR
 FRONT PLATE;
 CAN BE PLUGGED ONTO THE BASIC UNIT OR
 EXPANSION MODULE;
 10 LEDS FOR STATUS DISPLAY AND 5 USER-
 ASSIGNABLE KEYS FOR MANUAL CONTROL



General details:		
product brand name		SIRIUS
product designation		operator panels
Protection class IP / on the front		IP54
mounting position		any
Installation altitude / at a height over sea level / maximum	m	4,000
Ambient temperature		
• during storage	°C	-40 ... +80
• during operating	°C	-25 ... +60
• during transport	°C	-40 ... +80
Relative humidity		
• during operating phase	%	5 ... 95
EMC immunity to interference / according to IEC 60947-1		corresponds to degree of severity 3
Conductor-bound parasitic coupling BURST		1 kV
Conductor-bound parasitic coupling conductor-earth SURGE		
• according to IEC 61000-4-5		2 kV
Conductor-bound parasitic coupling conductor-conductor SURGE		
• according to IEC 61000-4-5		1 kV
Field-bound parasitic coupling		

• according to IEC 61000-4-3		10 V/m
Resistance against vibration		1-6 Hz / 15 mm; 6-500 Hz / 2 g
Impulse voltage resistance / rated value	V	4,000
Insulation voltage / rated value	V	300
Item designation		
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		A
• according to DIN EN 61346-2		A

Installation/mounting/dimensions:

Type of mounting		front mounting
Width	mm	96
Height	mm	36
Depth	mm	44

Certificates/approvals:

Verification of suitability CE / UL / CSA / CCC / C-TICK / GOST / NOM / ABS / DNV / GL / LRS / RoHS

General Product Approval

EMC

For use in hazardous locations



CCC



CSA



GOST



UL



C-TICK

[Explosion Protection Certificate](#)

Test Certificates

Shipping Approval

[Special Test Certificate](#)



ABS



DNV



GL

other

[Confirmation](#)

[Declaration of Conformity](#)



Profibus

[PROFINET-Certification](#)

[PROFISafe-Certification](#)

[other](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:



<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3UF7200-1AA00-0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3UF7200-1AA00-0



last change:

Jul 1, 2013