

## General Information

Extended Product Type:	PR30
Product ID:	1SNA173220R0500
EAN:	3472591732207
Catalog Description:	PR30 Prepunched symmetrical mounting rail

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Mounting Rails

## Ordering

EAN:	3472591732207
Minimum Order Quantity:	2 piece
Customs Tariff Number:	72166110

## Dimensions

Product Net Width:	2000 mm
Product Net Height:	35 mm
Product Net Length:	7.5 mm
Product Net Depth:	7.5 mm
Product Net Weight:	328 g

## Container Information

Package Level 1 Units:	2 piece
Package Level 1 Gross Weight:	0.656 kg
Package Level 1 EAN:	3472591732207
Package Level 2 Units:	40 piece
Product Packing Type:	Rail

## Additional Information

Function:	Mounting Rail
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Zinc plating and passivation steel
Medium Description:	Symmetrical mounting rail Dim 35 mm x 7.5 mm 1.379 in x 0.295 in Pre-punched for quick installation
Mounting Type:	- In order to guarantee the performances and security of your installation, please ensure the rail and its fixings can withstand the static and dynamic loads of the components mounted on it; - To prevent the rail from flexing (1 mm 0.039 in rail thickness only), fixing is recommended every 250 mm 9.84 in; - To prevent any issues during mounting, screw heads used for rail fixing should not protrude from the rail (7,5 mm 0.295 in rail height only).
Product Main Type:	PR
Product Name:	Mounting Rail
Rated Cross-Section:	10 mm <sup>2</sup>
Spacing:	2000 mm
Sub-Function:	TH 35-7.5
Suitable For:	BAM3 D35/16.PEN.2L D70/22 M6/8.ST ZDK2.5-22 ZDK4-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZDS4-22-R1 ZK10 ZK10-3P ZK10-PE ZK10-PE-3P ZK16 ZK16-3P ZK16-PE ZK16-PE-3P ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2

ZK2.5-D2-PE  
ZK2.5-D-CH  
ZK2.5-PE  
ZK2.5-PE-3P  
ZK2.5-PE-4P  
ZK2.5-S  
ZK2.5-SF  
ZK2.5-SF-R  
ZK2.5-SP  
ZK2.5-S-R1  
ZK4  
ZK4-3P  
ZK4-4P  
ZK4-PE  
ZK4-PE-3P  
ZK4-PE-4P  
ZK6  
ZK6-3P  
ZK6-PE  
ZK6-PE-3P  
ZP2.5  
ZP2.5-3P  
ZP2.5-4P  
ZP2.5-D1  
ZP2.5-D2  
ZP2.5-PE  
ZP2.5-PE-3P  
ZP2.5-PE-4P  
ZP2.5-S  
ZP2.5-SP  
ZS10  
ZS10-PE  
ZS10-S  
ZS10-SP  
ZS16  
ZS16-PE  
ZS25  
ZS35  
ZS35-PE  
ZS35-PEN  
ZS4  
ZS4-D1  
ZS4-D2  
ZS4-D2-S  
ZS4-D2-SF1  
ZS4-D2-SF1-R  
ZS4-D2-S-T  
ZS4-D-CH  
ZS4-PE  
ZS4-PE-R2  
ZS4-R1  
ZS4-R2  
ZS4-S  
ZS4-SF  
ZS4-SF1  
ZS4-SF1-R  
ZS4-SF1-T  
ZS4-SF-R  
ZS4-SF-T  
ZS4-SP  
ZS4-SP-R1  
ZS4-SP-T2  
ZS4-SP-T2-R1  
ZS4-S-R1  
ZS4-S-R2  
ZS4-S-R3  
ZS4-S-T  
ZS4-S-T-R1  
ZS4-T3  
ZS4-T3-R1  
ZS50  
ZS6  
ZS6-3S  
ZS6-3S-PE  
ZS6-4S  
ZS6-4S-PE  
ZS6-D1  
ZS6-D1-PE  
ZS6-D2  
ZS6-D2-PE  
ZS6-PE  
ZS6-S  
ZS6-S-4S-T  
ZS70  
ZS95

---

---

**Certificates and Declarations (Document Number)**

---

Data Sheet, Technical Information: 1SNK160017D0201

RoHS Information: 1SND230012F0203

---

**Classifications**

---

ETIM 4.0: EC001285 - Mounting rail

ETIM 5.0: EC001285 - Mounting rail

Object Classification Code: X

---

