

Scotch-Brite™

Hand Finishing Systems

Widest choice of hand pads for cleaning, scuffing, deburring, finishing, and other surface conditioning applications





Scotch-Brite™ Light Duty Cleansing Pad 7445 (white)

- Very mild abrasive for gentle, yet thorough cleaning
- Commonly used with liquid detergent
- Provides similar performance as steel wool grade 0000




Scotch-Brite™ Clear Blend Prep Scuff 7745 (gold)

- Ideal for top coat rubbing, sealer sanding prior to lacquer, and defuzzing or denibbing wood
- Provides similar performance as steel wool grade 000




Scotch-Brite™ Ultra Fine Hand Pad 7448 (gray)

- Ultra fine consistent finishes on metals, woods, plastics, and composites
- Provides similar performance as steel wool grade 00




Scotch-Brite™ General Purpose Hand Pad 7447 (maroon)

- Standard for surface conditioning worldwide
- Clean, blend, finish, and deburr faster, easier, and with better results than conventional abrasives
- Provides similar performance as steel wool grade 1



Scotch-Brite™ Production Hand Pad 8447 (maroon)

- High cut for paint preparation, blending, and scuffing
- Long life performance on aluminum, stainless steel, plastics, wood, and fiberglass
- Provides similar performance as steel wool grade 2



Scotch-Brite™ Blending Hand Pad 7446 (gray)

- Specially designed for hand blending and finishing stainless steel
- Mineral coarseness blends surface scratches on many metals, wood, and synthetic surfaces
- Provides similar performance as steel wool grade 3



Scotch-Brite™ Heavy Duty Hand Pad 7440 (tan)

- Most durable and aggressive pad for quick stock removal
- Cuts fast to remove contaminants and oxides in the most demanding cleaning and finishing applications
- Provides similar performance as steel wool grade 4

Less Aggressive = Finer Finish

More Aggressive = Coarser Finish

Multi-Flex Sheets — Highly Conformable Finishing

Scotch-Brite™ Multi-Flex Abrasive Sheet A ULF (gold)

- Ultra flexible and conformable abrasive for cleaning or fine finishing
- Provides similar performance as steel wool grade 000




Scotch-Brite™ Multi-Flex Abrasive Sheet S ULF (gray)

- Highly conformable abrasive with silicon carbide mineral for exceptional finishes on wood and metal
- Provides similar performance as steel wool grade 00



Scotch-Brite™ Multi-Flex Abrasive Sheet A VFN (dark maroon)

- Highly conformable abrasive with high cut for paint preparation and wood finishes without dumping edges
- Provides similar performance as steel wool grade 0



Scotch-Brite™ Clean & Finish Rolls

- Flexible web for finishing, blending and polishing
- Conformable for access to hard-to-reach areas
- Can be cut to desired length for hand sanding or oscillating sanders



Scotch-Brite™ Scrubbing Sponge 74 (Green)

- Highly conformable web laminate to a sponge backing
- Ideal for general purpose cleaning



Multi-purpose Trial Pack

An easy, inexpensive way to see how the many Scotch-Brite™ Hand Pads outperform steel wool, wire brushes, and other non-woven hand pads. The trial pack includes one each of the following:

- Scrubbing Sponge 74
- Light Duty Pad 6448
- Heavy Duty Pad 7440
- Light Duty Cleansing Pad 7445
- Blending Pad 7446
- General Purpose Pad 7447
- Ultra-Fine Pad 7448
- Production Pad 8447
- Twist-Lok™ Pad Holder 961

Scotch-Brite™ Product Ordering Information

Description	UPC	Color	Grade	Inner Quantity	Case Quantity
Light Duty Cleansing Pad 7445	048011-16976-7	○ white	F SFN	20/box	3 boxes/case
Ultra Fine Hand Pad 7448	048011-04028-8	● gray	S ULF	20/box	3 boxes/case
General Purpose Hand Pad 7447	048011-04029-5	● maroon	A VFN	20/box	3 boxes/case
Production Hand Pad 8447	048011-24037-4	● maroon	A VFN	20/box	3 boxes/case
Blending Hand Pad 7446	048011-04051-6	● gray	S MED	10/box	4 boxes/case
Heavy Duty Hand Pad 7440	048011-04050-9	● tan	A MED	10/box	4 boxes/case
Multi-Flex Abrasive Sheet Rolls	051131-07521-4	● dark maroon	A VFN	60 sheets/roll	4 rolls/case
	051131-07522-1	● gray	S ULF	60 sheets/roll	4 rolls/case
	051131-07523-8	● gold	A ULF	60 sheets/roll	4 rolls/case
Clear Blend Prep Scuff 7745	051131-07745-4	● gold	A ULF	4.75 in x 15 ft/roll	3 rolls/case
Clean & Finish Roll	048011-00264-4	● maroon	A MED	4 in x 30 ft/roll	3 rolls/case
	048011-00265-1	● maroon	A FIN	4 in x 30 ft/roll	3 rolls/case
	048011-00266-8	● maroon	A VFN	4 in x 30 ft/roll	3 rolls/case
	048011-00270-5	● gray	S VFN	4 in x 30 ft/roll	3 rolls/case
	048011-00274-3	● maroon	A MED	6 in x 30 ft/roll	2 rolls/case
	048011-00275-0	● maroon	A FIN	6 in x 30 ft/roll	2 rolls/case
	048011-00276-7	● maroon	A VFN	6 in x 30 ft/roll	2 rolls/case
Scrubbing Sponge 74	048011-20688-7	● green	A VFN	3.5 in x 6.1 in	20/case
Hand Pad Trial Pack 961S	048011-17144-9	—	—	—	5 packs
Twist-Lok™ Pad Holder 961	048011-09493-9	—	—	—	10/case

Product Use: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy: Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. **3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability: Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Business

Customer Response Center
900 Bush Avenue, Building 21-1W-10
St. Paul, MN 55106

Please Recycle

3M, Scotch-Brite and Twist-Lok are trademarks of 3M.

Printed in U.S.A.
61-5002-8008-8
© 3M 2006. All Rights Reserved.